

lifeAGLOW®

HINKLEY®
& FREDRICK RAMOND

HINKLEY & RR[®]

HINKLEY LIGHTING & FREDRICK RAMOND

CATALOG 2013 | 2014

LET HINKLEY TRANSPORT YOU INTO AN EXCITING NEW WORLD WHERE LIGHTING, DESIGN AND FASHION COME TOGETHER. FASHION HAS TAKEN ON AN INFLUENTIAL NEW ROLE IN INTERIOR DESIGN BY INSPIRING THE COLORS, SHAPES AND TEXTURES THAT CREATE THE UNIQUE MOOD AND ATMOSPHERE OF YOUR HOME.

AT HINKLEY, WE EMBRACE THE DESIGN PHILOSOPHY THAT YOU CAN MERGE TOGETHER THE LIGHTING, FURNITURE, ART, COLORS AND ACCESSORIES YOU LOVE INTO A BEAUTIFUL ENVIRONMENT THAT DEFINES YOUR OWN PERSONAL STYLE. WE HOPE YOU WILL BE INSPIRED BY OUR COMMITMENT TO KEEP YOUR 'LIFE AGLOW.'

THIS CATALOG INCLUDES THE FULL RANGE OF INTERIOR AND EXTERIOR LIGHTING FROM HINKLEY LIGHTING AS WELL AS THE FULL LINE FROM FREDRICK RAMOND. FOR LANDSCAPE LIGHTING, SEE OUR FULL LINE HINKLEY LANDSCAPE LIGHTING CATALOG.

HINKLEY LIGHTING, INC.

ONE FAMILY, THREE BRANDS : A FULL SPECTRUM OF LIGHTING



HINKLEY LIGHTING : CLASSIC, TIMELESS COLLECTIONS FEATURING A VARIETY OF DESIGNS RANGING FROM TRADITIONAL TO CONTEMPORARY.




Fixtures shown: Dunhill 4598 RY, page 153 and Luna 1647 SW, page 442




FREDRICK RAMOND : CHIC, FASHIONABLE LIGHTING WITH A FOCUS ON MODERN ELEGANCE AND LUXURIOUS DETAILS.





HINKLEY LANDSCAPE LIGHTING : COMBINING SOPHISTICATION WITH DURABILITY, THIS COLLECTION COMPLEMENTS OUR OUTDOOR LIGHTING FAMILIES AND PROVIDES THE LATEST TECHNOLOGY AND OUTSTANDING WORKMANSHIP.





— FAMILY OWNED & OPERATED SINCE 1922 —

THE LEGACY CONTINUES

FROM LEFT : ERIC WIEDEMER, LEGAL COUNSEL; RICK WIEDEMER, PRESIDENT; JESS WIEDEMER, VICE PRESIDENT OF OPERATIONS

“AS A FOURTH GENERATION COMPANY WE ARE PROUD TO BLEND OUR HERITAGE AND INNOVATIVE SPIRIT TO PROVIDE THE MOST EXCITING, FASHION-FORWARD AND TECHNOLOGICALLY ADVANCED LIGHTING POSSIBLE.”

RICK WIEDEMER, PRESIDENT
HINKLEY LIGHTING, INC. | CLEVELAND, OHIO


Under four generations of family leadership, Hinkley Lighting has transformed from a small outdoor lantern company to a global brand intent on bringing you the best in style, quality and value. We thrive on personal relationships, regional roots, inspiring design and a family atmosphere that is encouraged at every level of our company. If the past 90 years are any indication, it is with great pride and excitement that we set our sights on the horizon and extend our commitment to keeping your ‘Life Aglow.’

SCAN THE MOBI TAG WITH YOUR SMART PHONE OR
TABLET TO WATCH OUR “THIS IS HINKLEY” VIDEO.
GET THE APP: gettag.mobi





C A T A L O G
VIDEO TOUR



SCAN WITH YOUR SMART
PHONE OR TABLET TO
WATCH A VIDEO TOUR OF
THIS CATALOG.
GET THE APP: gettag.mobi

I AM PLEASED TO SHARE OUR NEW HINKLEY AND FREDRICK RAMOND CATALOG. Inside these pages you will discover how our passion for style, our pursuit of innovative design and our quest for state-of-the-art technology merge to fulfill all your lighting needs. A unique Pictorial Index, starting on page 10, gives a quick overview of our product offerings. Each collection is presented in an easy-to-understand format to simplify your selection process, while product video icons allow you to experience informational virtual overviews.

Hinkley's "Design Centers," our collaboration with nationally-recognized designers, editors, stylists and bloggers (see page 38), continues in our print and digital catalog editions and on hinkleylighting.com. We are thrilled to partner with these acclaimed home decor experts and deliver helpful recommendations and insider tips directly to you. To make your research process even more enjoyable, look for our "Style Guides" and fashion-forward lifestyle photography to inspire your creativity and reveal the significant and exciting relationship between lighting and interior design.

Now is a time of unprecedented access to information about companies and their products and we offer a 360° engagement with the Hinkley brands to stimulate and educate your lighting selection. To connect with us, visit the inside back cover of this catalog and learn why "This is Hinkley."

We hope you enjoy your Hinkley experience.

RICK WIEDEMER, PRESIDENT
HINKLEY LIGHTING, INC. | CLEVELAND, OHIO

HINKLEY CHANDELIER COLLECTIONS

<i>Design Center</i>	040
AMELIA	211
BOLLA	108
BRANTLEY	122
CAMBRIDGE	180
CARLTON	206
CASA	140
CELLO	162
CHANNING	078
CIRRUS	098
CONGRESS	214
CORDILLERA	104
DARIEN	080
DILLON	082
DUNHILL	152
FLOURISH	096
GENTRY	176
HADLEY	232
HAMPTON	090
HARLOW	050
HARPER	226
HATHAWAY	102
HUTTON	230
LANDON	168
LANZA	100
LAUREN	136
MARCELLINA	204
MARGEAUX	058
MARION	138
MAYFLOWER	156
MERIDIAN	064
MIDTOWN	070
MONACO	074
MONDRIAN	106
PARKER	128
PELHAM	228
PIPER	072
PLANTATION	196
PLYMOUTH	158
PRINCETON	062
ROCKFORD	190
SLOAN	144
SPLENDOR	048
STOWE	134
SUSSEX	146
THISTLEDOWN	130
TRUMAN	154
VALLEY	086
VERANDA	208
VICTORY	084
VIRGINIAN	192
WHITNEY	120
WINGATE	170
YORKTOWN	164
ZELDA	054



FREDRICK RAMOND

ALEXANDRA	260
AVA	300
BARCELONA	270
BENTLEY	284
BIJOU	258
BROADWAY	252
CALISTA	250
CAMERON	292
CARABEL	273
CASPIA	268
CELESTE	276
FRANCESCA	266
GLOBE	312
HAMLET	294
ION	248
JASPER	302
KARMA	244
KINGSLEY	282
LOFT	308
LUXE	316
MIDDLEFIELD	296
MIME	262
MONDO	242
MONTEREY	280
MUSE	278
NEST	289
OMNI	240
PANDORA	286
PROSECCO	256
QUATTRO	247
RENATA	298
SPECTRA	310
STRATUS	313
VIVO	314
XANADU	254
ZEN	304
ACCESSORIES	318
HINKLEY BATH COLLECTIONS	
<i>Design Center</i>	322
ABBIE	376
ADELE	340
ALICE	374
ANNA	348
ASHBURY	343
ASHLEY	333
AVON	336
BOLLA	388
BRANTLEY	383
BROOKE	386
CASA	394
DAPHNE	350
DARIA	356
DUET	357
ELEMENT	365
ENVY	346

FLYNN	395
FRANCOISE	398
ISABELLA	396
JORDAN	370
JOSIE	341
JULES	360
KATIA	334
LANZA	372
LATITUDE	361
LOLA	362
MASON	369
MERIDIAN	366
MIA	371
MILEY	330
MIRA FIZZ	355
MIRA MESH	353
NEST	393
OCHO	342
OMNI	335
PINNACLE	338
PLANTATION	400
PLYMOUTH	391
REESE	387
SAN SIMEON	402
SHELLY	380
SOPHIE	364
STOWE	392
TAYLOR	344
TORY	382
WINTON	358
YORKTOWN	384
ZARA	349
ZINA	363

HINKLEY OUTDOOR COLLECTIONS

<i>Design Center</i>	404
ARIA	450
ATLANTIS	422
AUGUSTA	578
AURORA	490
BARRINGTON	570
BINGHAM	518
BOLLA	486
BRIGHTON	508
BRYNMAR	598
CAMELOT	532
CAPE COD	494
CASA	554
CASCADE	432
CASTELLE	482
CEDAR HILL	540
CHERRY CREEK	544
CHESTERFIELD	564
CLIFTON BEACH	594
CLIFTON PARK	596
CORDILLERA	556
DISTRICT	420
DORIAN	446
EDGEWATER	530
ELM	552
FORUM	584
FREEPORT	464
GRAYSON	492
HARBOR	468
HOLBROOK	550
KEY WEST	574
KUBE	436
LEDGEWOOD	478
LIBERTY	502
LUCERNE	576
LUNA	440
MANHATTAN	476
MANOR HOUSE	528
MONDRIAN	475
MONTAUK	504
MONTICELLO	592
MONTREAL	606
NANTUCKET	506
NEW CASTLE	496
OXFORD	572
PEMBROOK	462
PLANTATION	608
PUTNEY BRIDGE	512
RALEY	526
RANDOLPH	536
REEF	460
REGAL	534
REVERE	516
RICHMOND	524
ROWE PARK	600
SAN CLEMENTE	588
SATURN	416
SEDGWICK	514
SENATOR	523
SHELTER	452
SIERRA	474
SOLARA	448
SORRENTO	604
STRATFORD	542
SULLIVAN	458
SURF	414
TAHOE	548
THISTLEDOWN	558
TITAN	444
TRAFALGER	562
TRELLIS	566
VALLEY FORGE	510
WABASH	560
WESTWINDS	498
WINDSOR	580
YORK	520
ECO DETAILS	413
POSTS & PIER MOUNTS	613
HINKLEY LANDSCAPE LIGHTING	430

Location Photography:
Rob Brinson Photography

Product Photography:
Richard Kronenberg Photography

Throughout this catalog we have utilized a variety of important icons and finish codes to assist you with your lighting selections. Below is a key describing each of these icons in detail as well as a list of our extensive product finishes with abbreviated codes for easy reference.



ADA COMPLIANT

Indicates fixtures that adhere to the standards and guidelines listed by the Americans with Disabilities Act.



COMBINATION MOUNT

Indicates fixtures that are supplied with the means to be chain hung or mounted flush to the ceiling.



DARK SKY

Indicates fixtures that are engineered to minimize light glare upward into the night sky.



DIFFUSER INCLUDED

Indicates fixtures that come equipped with a diffuser to minimize bulb exposure and soften the intensity of light omitted.



DAMP LOCATION

Indicates fixtures that can withstand indirect moisture in a protected or sheltered environment.



FIXTURE EXCEEDS 50LBS.

Indicates fixtures weighing over 50lbs. Fixtures must be supported independently of the outlet box unless the outlet box is UL listed for the appropriate weight. Required hardware included.



GU24

Energy-efficient socket accepts LED and fluorescent lamps



INVISI-MOUNT

Indicates fixtures where the mounting hardware is hidden on the back plate.



LED

Fixtures come equipped with a fully integrated LED panel and built-in driver.



OVAL-SHAPED FIXTURE

Indicates chandeliers that are oval in shape.



SELECT-A-LITE

Indicates fixtures that come with sockets that can accept either candelabra or medium-based bulbs.

HINKLEY FINISHES

AI	AGED IRON	BZ	BRONZE	MR	MUSEUM BRONZE	RY	ROYAL BRONZE
AM	AUTUMN	CB	COPPER BRONZE	MT	METRO BRONZE	SB	SPANISH BRONZE
AN	ANTIQUENICKEL	CL	CHARCOAL	OB	OLDE BRONZE	SK	SATIN BLACK
AP	ANTIQUENICKEL	CM	CHROME	OL	OLDE BLACK	SL	SILVER LEAF
AR	ANCHOR BRONZE	EZ	ENGLISH BRONZE	OP	OLDE PENNY	SN	SIENNA
AS	AGED BRASS	FB	FORUM BRONZE	OZ	OIL RUBBED BRONZE	SS	STAINLESS STEEL
AT	ANTIQUENICKEL	FZ	FRENCH BRONZE	PB	POLISHED BRASS	SU	SUMMERSTONE
BB	BURNISHED BRASS	GR	GOLDEN BRONZE	PL	POLISHED ANTIQUENICKEL	SW	SATIN WHITE
BC	BURNISHED BRASS	HE	HEMATITE	PN	POLISHED NICKEL	SZ	SIENNA BRONZE
BG	BLACK GRANITE	KZ	BUCKEYE BRONZE	PW	PEWTER	TB	TEXTURED BLACK
BH	BLACKSMITH	MB	MUSEUM BLACK	PZ	PEARL BRONZE	TT	TITANIUM
BK	BLACK	MC	METRO COPPER	RB	REGENCY BRONZE	VK	VINTAGE BLACK
BN	BRUSHED NICKEL	MN	MIDNIGHT BRONZE	RI	RUSTIC IRON	VS	VINTAGE BRASS
BR	BRUSHED BRONZE	MO	MOCHA	RK	RIVER ROCK	VZ	VICTORIAN BRONZE

FREDRICK RAMOND

ANB	ANODIZED BLACK	BME	BRUSHED MERLOT	PBA	POLISHED AND BRUSHED ALUMINUM
ANG	ANODIZED GOLD	BNI	BRUSHED NICKEL	PCM	POLISHED CHROME
ANS	ANODIZED SILVER	BRC	BRUSHED CINNAMON	PNI	POLISHED NICKEL
BAM	BAMBOO	CHY	CHERRY	PSS	POLISHED STAINLESS STEEL
BBA	BRUSHED ALUMINUM AND BRUSHED BRONZE	CLD	CLOUD	PTR	PEWTER
BBZ	BRUSHED BRONZE	FBZ	FRENCH BRONZE	RCO	RENAISSANCE COPPER
BCH	BRUSHED CHAMPAGNE	FRM	FRENCH MARBLE	RBR	RETRO BRASS
BKS	BLACKSMITH	IRN	RUSTIC IRON	SLF	SILVER LEAF
BLI	BLACK IRON WITH ANTIQUE SILVER HIGHLIGHTS	IRR	IRON RUST	VBZ	VINTAGE BRONZE
BLK	BLACK	MPL	MAPLE	WAL	WALNUT
		ORB	OIL RUBBED BRONZE		
		PAL	POLISHED ALUMINUM		



Fixtures shown: Freeport 1802 OP, page 467

A brief glossary of common lighting TERMS

FLUSH OR SEMI-FLUSH MOUNT

Sometimes referred to as ceiling mounted fixtures, these fixtures mount directly to the ceiling with a “pan” or canopy.

GLASS OR SHADE A decorative opaque or translucent covering on light fixtures designed to shield the light source or redirect the light.

LED Light emitting diode. Extremely efficient and long lasting solid state lighting. Estimated LED chip life = 40,000 hrs.

PENDANT These fixtures can be used to provide both task and general lighting. Equipped with shades or globes to avoid glare, they are suspended from the ceiling over tables, kitchen counters or other work areas.

SCONCE An ornamental light fixture attached to a wall to provide additional layers of light in a room.

TASK LIGHTING Lighting that is specifically installed to light an area where a task is performed.

TOP TO OUTLET (TTO) The measurement from the top of the fixture to the center of the outlet box when installed.

TRANSFORMER An electrical device that transforms the line voltage (usually 120 volts for residential settings or 277 volts for commercial settings) into the voltage that a low voltage lighting system requires (12, 15 or 24 volts).

WATTAGE The amount of energy consumed by a light bulb.

ACCENT LIGHTING Lighting that is used to accent or highlight a particular object such as a work of art. To be effective accent lighting should be approximately four or five times the level of ambient light in the room.

ADA (Americans with Disabilities Act): ADA compliant fixtures do not extend more than 4” from the wall.

AMBIENT LIGHTING General lighting that usually lights up an entire space.

ARM A decorative shaped tube or casting that is used to support a socket that usually has socket wires running through it.

BACK PLATE The part of a fixture that mounts to a wall or vertical surface.

BOBESCHE A disc or decorative plate that sits under the candle sleeve.

CANOPY The decorative plate that attaches to ceiling to cover the junction box.

COMBINATION MOUNT Refers to the ability of a fixture to either be hung by chain or mounted directly to the ceiling.

COMPACT FLUORESCENT (CFL) An energy efficient fluorescent bulb with a lifespan that is 10 times longer and 3 to 4 times more efficient than an incandescent bulb.

DIFFUSER A shield or shade that softens light intensity and/or prevents the light bulbs from being directly exposed.

DIMMER A device used for varying the brightness of lamps in a lighting installation. Dimming controls are ideal for almost any type of room because they can change the amount of lighting to suit each mood or activity.

EXTENSION Refers to the depth of a wall mounted fixture or the measurement from the wall to the farthest point on the fixture away from the wall.

FINIAL A small finishing ornament at the crown or bottom of a fixture.

CHANDELIERS HINKLEY & FREDRICK RAMOND



ALEXANDRA
Pages 260-261
Polished Nickel



AVA
Pages 300-301
Vintage Bronze



BARCELONA
Pages 270-272
French Marble



BENTLEY
Pages 284-285
Brushed Bronze



BIJOU
Pages 258-259
Polished Nickel



BOLLA
Pages 108-111
Brushed Nickel



BOLLA
Pages 116-119
Brushed Bronze



BOLLA
Pages 112-115
Olde Bronze



BRANTLEY
Pages 122-123
Brushed Nickel



BRANTLEY
Pages 124-125
Oil Rubbed Bronze



BRANTLEY
Pages 126-127
Textured Black



BROADWAY
Pages 252-253
Polished Aluminum



CALISTA
Pages 250-251
Brushed Nickel



CAMBRIDGE
Pages 180-182
Burnished Brass



CAMBRIDGE
Pages 183-185
Olde Bronze



CAMBRIDGE
Pages 186-188
Pewter



CAMERON
Pages 292-293
Polished Chrome



CARABEL
Pages 273-275
Brushed Champagne



CARLTON
Pages 206-207
Silver Leaf



CASA
Pages 140-143
Olde Black



CASPIA
Pages 268-269
Silver Leaf



CELESTE
Pages 276-277
Silver Leaf



CELLO
Pages 162-163
Antique Bronze



CHANNING
Pages 78-79
Brushed Nickel



CIRRUS
Pages 98-99
Brushed Nickel

HINKLEY & FREDRICK RAMOND CHANDELIERS



CORDILLERA
Pages 104-105
Rustic Iron



DARIEN
Pages 80-81
Polished Antique Nickel



DILLON
Pages 82-83
Brushed Nickel



DUNHILL
Pages 152-153
Royal Bronze



FLOURISH
Pages 96-97
Silver Leaf



FRANCESCA
Pages 266-267
Silver Leaf



GENTRY
Pages 176-177
Pewter



GENTRY
Pages 178-179
Polished Brass



HADLEY
Pages 234-235
Antique Nickel



HADLEY
Pages 234-235
Brushed Bronze



HADLEY
Pages 234-235
Chrome



HADLEY
Pages 234-235
Oil Rubbed Bronze



HAMLET
Pages 294-295
Vintage Bronze



HAMPTON
Pages 90-92
Antique Nickel



HAMPTON
Pages 93-95
Brushed Bronze



HARLOW
Pages 52-53
Brushed Caramel



HARLOW
Pages 50-51
Polished Nickel



HATHAWAY
Pages 102-103
Antique Nickel



HATHAWAY
Pages 102-103
Olde Bronze



ION
Pages 248-249
Anodized Black



ION
Pages 248-249
Anodized Gold



ION
Pages 248-249
Anodized Silver



JASPER
Pages 302-303
Rustic Iron



KARMA
Pages 244-246
Polished Aluminum



KINGSLEY
Pages 282-283
Silver Leaf

CHANDELIERS HINKLEY & FREDRICK RAMOND



LANDON
Pages 168-169
Brushed Nickel



LANZA
Pages 100-101
Oil Rubbed Bronze



LAUREN
Pages 136-137
Victorian Bronze



MARCELLINA
Pages 204-205
Golden Bronze



MARGEAUX
Pages 58-59
Polished Nickel



MARGEAUX
Pages 60-61
Vintage Brass



MARION
Pages 138-139
Textured Black



MAYFLOWER
Pages 156-157
Olde Bronze



MERIDIAN
Pages 66-69
Brushed Nickel



MERIDIAN
Pages 66-68
Satin Black



MIDDLEFIELD
Pages 296-297
Iron Rust



MIDTOWN
Pages 70-71
Brushed Nickel



MIME
Pages 262-263
Polished Nickel



MIME
Pages 264-265
French Bronze



MONACO
Pages 76-77
Brushed Caramel



MONACO
Pages 74-75
Brushed Nickel



MONDO
Pages 242-243
Polished Chrome



MONDRIAN
Pages 106-107
Buckeye Bronze



MONTEREY
Pages 280-281
Brushed Merlot




MUSE
Pages 278-279
Blacksmith



NEST
Pages 289-291
Oil Rubbed Bronze



OMNI
Pages 240-241
Polished Nickel



PANDORA
Pages 286-288
Brushed Cinnamon



PARKER
Pages 128-129
Buckeye Bronze



PIPER
Pages 72-73
Brushed Nickel

HINKLEY & FREDRICK RAMOND CHANDELIERS



PLANTATION
Pages 198-200
Burnished Brass



PLANTATION
Pages 196-197
Polished Antique Nickel



PLANTATION
Pages 201-203
Pearl Bronze



PLYMOUTH
Pages 158-161
Olde Bronze



PRINCETON
Pages 62-63
Brushed Nickel



PROSECCO
Pages 256-257
Renaissance Copper



QUATTRO
Page 247
Brushed Nickel



RENATA
Pages 298-299
Blacksmith



ROCKFORD
Pages 190-191
Forum Bronze



SLOAN
Pages 144-145
Regency Bronze



SPECTRA
Pages 310-311
Black



SPECTRA
Pages 310-311
Cloud



SPECTRA
Pages 310-311
Pewter



SPECTRA
Pages 310-311
Retro Brass



SPLENDOR
Pages 48-49
Brushed Nickel



STOWE
Pages 134-135
Metro Copper



SUSSEX
Pages 146-148
Brushed Nickel



SUSSEX
Pages 149-151
English Bronze



THISTLEDOWN
Pages 130-132
Victorian Bronze



TRUMAN
Pages 154-155
Antique Nickel



VALLEY
Pages 86-87
Brushed Nickel



VALLEY
Pages 88-89
Vintage Black



VERANDA
Pages 208-209
Summerstone



VICTORY
Pages 84-85
Brushed Nickel



VIRGINIAN
Pages 192-193
Polished Brass

CHANDELIERS HINKLEY & FREDRICK RAMOND



VIRGINIAN
Pages 194-195
Pewter



WHITNEY
Pages 120-121
Brushed Nickel



WINGATE
Pages 170-172
Polished Antique Nickel



WINGATE
Pages 173-175
Oil Rubbed Bronze



XANADU
Pages 254-255
Polished Stainless Steel



YORKTOWN
Pages 164-165
Antique Nickel




YORKTOWN
Pages 166-167
Brushed Bronze



ZELDA
Pages 54-55
Polished Nickel



ZELDA
Pages 56-57
Vintage Brass



ZEN
Pages 304-305
Bamboo

SCONCES HINKLEY & FREDRICK RAMOND



52700BN
Adele, Page 340
4 1/4" W, 9" H
Brushed Nickel



5850
Abbie, Pages 376-378
6 3/4" W, 7 3/4" H
Brushed Caramel,
Brushed Nickel, Chrome



FR43622PNI
Alexandra, Page 261
11 1/2" W, 12 3/4" H
Polished Nickel



5830
Alice, Pages 374-375
5 1/4" W, 8 3/4" H
Antique Nickel,
Brushed Bronze



5780CM
Anna, Page 348
6" W, 8 3/4" H
Chrome



5700CM
Ashbury, Page 343
6" W, 8" H
Chrome



5190CM
Ashley, Page 333
5" W, 8 1/2" H
Chrome



5550
Avon, Page 336-337
7 3/4" W, 7 1/2" H
Brushed Nickel, Chrome



FR42872VBZ
Ava, Page 301
9" W, 12" H
Vintage Bronze




FR44106FRM
Barcelona, Page 272
17 1/2" W, 19 1/2" H
French Marble



FR44110FRM
Barcelona, Page 272
12" W, 23" H
French Marble



FR44500BBZ
Bentley, Page 285
5 3/4" W, 18" H
Brushed Bronze



FR44502BBZ
Bentley, Page 285
14" W, 17" H
Brushed Bronze



FR43530PNI
Bijou, Page 259
16" W, 22" H
Polished Nickel



4650
Bolla, Pages 110, 114, 118, 388-390
7 3/4" W, 8 1/2" H
Brushed Nickel, Brushed
Bronze, Olde Bronze



4670
Bolla, Pages 110, 114, 118
7 3/4" W, 20 1/2" H
Brushed Nickel, Brushed
Bronze, Olde Bronze



4630
Brantley, Pages 123, 125, 127, 383
4 3/4" W, 12 1/4" H
Brushed Nickel, Oil Rubbed Bronze,
Textured Black



FR41430PAL
Broadway, Page 253
8" W, 5 1/4" H
Polished Aluminum



FR41431PAL
Broadway, Page 253
8" W, 8 1/2" H
Polished Aluminum



5000AN
Brooke, Page 386
5 1/4" W, 11 1/2" H
Antique Nickel



FR40100BNI
Calista, Page 251
8 3/4" W, 25" H
Brushed Nickel



FR40102BNI
Calista, Page 251
8 3/4" W, 25" H
Brushed Nickel



4410
Cambridge, Pages 181, 184, 187
4 1/2" W, 11" H
Burnished Brass,
Olde Bronze, Pewter



4412
Cambridge, Pages 181, 184, 187
15" W, 11" H
Burnished Brass,
Olde Bronze, Pewter



4640BB
Cambridge, Page 182
4 1/2" W, 13" H
Burnished Brass



4642BB
Cambridge, Page 182
14" W, 13 1/2" H
Burnished Brass



FR42340PCM
Cameron, Page 293
8" W, 17 1/2" H
Polished Chrome



FR44620BCH
Carabel, Page 275
12 3/4" W, 10 3/4" H
Brushed Champagne



4772SL
Carlton, Page 207
13 1/2" W, 19" H
Silver Leaf



4010OL
Casa, Pages 142, 394
5" W, 10 3/4" H
Olde Black



FR43752SLF
Caspia, Page 269
12" W, 6 1/2" H
Silver Leaf



FR42640SLF
Celeste, Page 277
6 1/2" W, 23 1/2" H
Silver Leaf



FR42642SLF
Celeste, Page 277
15 1/2" W, 19" H
Silver Leaf



5450AT
Cello, Page 163
8 1/2" W, 8 3/4" H
Antique Bronze



4220BN
Channing, Page 79
4 1/2" W, 18 1/2" H
Brushed Nickel

SCONCES HINKLEY & FREDRICK RAMOND



3170
Congress, Page 221
8" W, 11¾" H
Antique Nickel,
Brushed Caramel, Chrome,
Oil Rubbed Bronze



3171
Congress, Page 220
8¾" W, 13" H
Antique Nickel,
Brushed Caramel, Chrome,
Oil Rubbed Bronze



3172
Congress, Page 221
6" W, 14" H
Antique Nickel,
Brushed Caramel, Chrome,
Oil Rubbed Bronze



3173
Congress, Page 220
7" W, 13½" H
Antique Nickel,
Brushed Caramel, Chrome,
Oil Rubbed Bronze



3174
Congress, Page 220
7" W, 13½" H
Antique Nickel,
Brushed Caramel, Chrome,
Oil Rubbed Bronze



3175
Congress, Page 220
8¾" W, 13" H
Antique Nickel,
Brushed Caramel, Chrome,
Oil Rubbed Bronze



3176
Congress, Page 221
8" W, 11¼" H
Antique Nickel,
Brushed Caramel, Chrome,
Oil Rubbed Bronze



3177
Congress, Page 221
6" W, 14" H
Antique Nickel,
Brushed Caramel, Chrome,
Oil Rubbed Bronze



3178
Congress, Page 222
9¾" W, 12¾" H
Antique Nickel,
Brushed Caramel, Chrome,
Oil Rubbed Bronze



4090RI
Cordillera, Page 105
7½" W, 22" H
Rustic Iron



3960PL
Darren, Page 81
6¾" W, 15½" H
Polished Antique Nickel



3660BN
Dillon, Page 83
6" W, 7¾" H
Brushed Nickel



4590RY
Dunhill, Page 153
6¾" W, 11¼" H
Royal Bronze



5220BN
Element, Page 365
5¼" W, 7" H
Brushed Nickel



5910
Envy, Pages 346-347
6" W, 7¾" H
Brushed Nickel, Chrome



5820BH
Flynn, Page 395
7¾" W, 4½" H
Blacksmith



FR40312SLF
Francesca, Page 267
12" W, 22½" H
Silver Leaf



5580
Francoise, Pages 398-399
6" W, 10¾" H
Burnished Brass,
Polished Antique Nickel



FR42862VBZ
Hamlet, Page 295
10½" W, 16" H
Vintage Bronze




3202
Hampton, Pages 92, 95
15" W, 12" H
Antique Nickel,
Brushed Bronze



3210
Hampton, Pages 92, 95
6¾" W, 12" H
Antique Nickel,
Brushed Bronze



4210
Harlow, Pages 51, 53
4½" W, 14¾" H
Brushed Caramel,
Polished Nickel



FR36501
Ion, Page 249
21" W, 21" H
Anodized Black, Anodized
Gold, Anodized Silver



5390
Isabella, Pages 396-397
5½" W, 10" H
Burnished Brass,
Polished Antique Nickel



FR40200IRN
Jasper, Page 303
5" W, 10" H
Rustic Iron



FR40203IRN
Jasper, Page 303
5" W, 30" H
Rustic Iron



51350BN
Jordan, Page 370
4½" W, 7½" H
Brushed Nickel



5370BN
Josie, Page 341
4½" W, 8½" H
Brushed Nickel



53240BN
Jules, Page 360
5" W, 15½" H
Brushed Nickel



50200CM
Katia, Page 334
6" W, 6¾" H
Chrome



FR42720SLF
Kingsley, Page 283
9" W, 18¾" H
Silver Leaf



5100
Lanza, Page 372-373
7¼" W, 12" H
Antique Nickel,
Brushed Bronze



5650BN
Latitude, Page 361
5" W, 8" H
Brushed Nickel



4060VZ
Lauren, Page 137
6" W, 14¼" H
Victorian Bronze



5770BN
Lola, Page 362
5½" W, 10" H
Brushed Nickel



4400GR
Marcellina, Page 205
6½" W, 19" H
Golden Bronze



3580
Margeaux, Pages 59, 61
4½" W, 17¾" H
Polished Nickel,
Vintage Brass



3582
Margeaux, Pages 59, 61
12¾" W, 17¾" H
Polished Nickel,
Vintage Brass



4470TB
Marion, Page 139
4½" W, 17" H
Textured Black



5690TB
Mason, Page 369
9¼" W, 4½" H
Textured Black



5670OB
Mayflower, Page 157
5" W, 10½" H
Olde Bronze



3870
Meridian, Page 65, 69
5" W, 11¼" H
Brushed Nickel, Satin Black



5590
Meridian, Pages 65, 69, 366-368
5" W, 8" H
Brushed Nickel,
Chrome, Satin Black



5340BN
Mia, Page 371
6½" W, 7¾" H
Brushed Nickel



FR40570IRR
Middlefield, Page 297
5" W, 16½" H
Iron Rust



4970BN
Midtown, Page 71
5" W, 8" H
Brushed Nickel



5050
Miley, Pages 330-332
4½" W, 6½" H
Brushed Nickel,
Brushed Caramel, Chrome



FR45602
Mime, Pages 263, 265
14" W, 20½" H
Brushed Nickel,
French Bronze



4850
Monaco, Pages 75, 77
6¾" W, 10¾" H
Brushed Caramel,
Brushed Nickel




4852
Monaco, Pages 75, 77
20" W, 10¾" H
Brushed Caramel,
Brushed Nickel

SCONCES HINKLEY & FREDRICK RAMOND

PICTORIAL INDEX



4851
Monaco, Pages 75, 77
5" W, 20" H
Brushed Caramel,
Brushed Nickel



FR49292PCM
Mondo, Page 243
10½" W, 20" H
Polished Chrome



FR42500BME
Monterey, Page 281
10" W, 20" H
Brushed Merlot



FR40600BKS
Muse, Page 279
9¾" W, 20" H
Blacksmith



FR41610ORB
Nest, Page 291
12" W, 9" H
Oil Rubbed Bronze



FR41612ORB
Nest, Page 291
9" W, 14" H
Oil Rubbed Bronze



FR52202ORB
Nest, Page 393
5½" W, 24" H
Oil Rubbed Bronze



5420CM
Ocho, Page 342
6" W, 6" H
Chrome



FR42400BRC
Pandora, Page 288
9¾" W, 13" H
Brushed Cinnamon



4430KZ
Parker, Page 129
5¼" W, 12" H
Buckeye Bronze



5250
Pinnacle, Pages 338-339
5" W, 9" H
Antique Nickel, Chrome



4860BN
Piper, Page 73
4½" W, 12¾" H
Brushed Nickel



4140
Plantation, Pages 199, 202
6" W, 14½" H
Burnished Brass,
Pearl Bronze



4880
Plantation, Pages 197, 199, 202
6" W, 15" H
Burnished Brass, Polished
Antique Nickel, Pearl Bronze



5310
Plantation, Pages 197,
200, 203, 400-401
5" W, 8¾" H
Burnished Brass, Polished
Antique Nickel, Pearl Bronze



4240OB
Plymouth, Page 160
6½" W, 14" H
Olde Bronze



5470OB
Plymouth, Pages 160, 391
5½" W, 9¾" H
Olde Bronze



4070BN
Princeton, Page 63
5½" W, 16¾" H
Brushed Nickel



FR49430RCO
Prosecco, Page 257
12½" W, 22¾" H
Renaissance Copper



FR49450BNI
Quattro, Page 247
12" W, 15¾" H
Brushed Nickel



4620FB
Rockford, Page 191
5" W, 13" H
Forum Bronze



4622FB
Rockford, Page 191
14" W, 13½" H
Forum Bronze



56320AN
Reese, Page 387
5" W, 13½" H
Antique Nickel



5010
Shelly, Pages 380-381
5½" W, 9½" H
Brushed Nickel, Chrome



FR49190SLF
San Simeon, Page 402
6" W, 24½" H
Silver Leaf



4540RB
Sloan, Page 145
4¾" W, 16" H
Regency Bronze



54680BN
Sophie, Page 364
4½" W, 6½" H
Brushed Nickel



4922BN
Splendor, Page 49
14" W, 14" H
Brushed Nickel



4720MC
Stowe, Pages 135, 392
5" W, 14" H
Metro Copper



4790
Sussex, Pages 147, 150
4½" W, 17¾" H
Brushed Nickel,
English Bronze



4792
Sussex, Pages 147, 150
15½" W, 15¾" H
Brushed Nickel,
English Bronze



5020
Taylor, Pages 344-345
7¾" W, 6" H
Brushed Nickel, Chrome



5680VZ
Thistledown, Page 132
5¾" W, 12¾" H
Victorian Bronze



5200BN
Tory, Page 382
6¾" W, 9¼" H
Brushed Nickel



4020AN
Truman, Page 155
5¼" W, 12¾" H
Antique Nickel



4700
Valley, Page 87, 89
5¾" W, 21" H
Brushed Nickel,
Vintage Black



4802SU
Veranda, Page 209
14½" W, 17¾" H
Summerstone



4130BN
Victory, Page 85
6" W, 15¼" H
Brushed Nickel



5120
Virginian, Page 193, 195
4¾" W, 11" H
Polished Brass, Pewter



5124
Virginian, Page 193, 195
11" W, 11" H
Polished Brass, Pewter



4610BN
Whitney, Page 121
9" W, 15" H
Brushed Nickel



3002
Wingate, Pages 172, 175
10" W, 12½" H
Oil Rubbed Bronze,
Polished Antique Nickel



FR43355PSS
Xanadu, Page 255
18" W, 20½" H
Polished Stainless Steel



3620
Yorktown, Pages 165, 167
4¾" W, 13" H
Antique Nickel,
Brushed Bronze



3622
Yorktown, Pages 165, 167
13¾" W, 15" H
Antique Nickel,
Brushed Bronze



5740
Yorktown, Pages 384-385
4¾" W, 11" H
Antique Nickel,
Brushed Bronze



3440
Zelda, Pages 55, 57
5½" W, 11¾" H
Polished Nickel,
Vintage Brass



FR46200BAM
Zen, Page 305
6¾" W, 12" H
Bamboo



51560BN
Zina, Page 363
5" W, 7½" H
Brushed Nickel



ADA COMPLIANT SCONCES HINKLEY & FREDRICK RAMOND

PICTORIAL INDEX



1645, 1646
Atlantis, Pages 423,425,427,429
9" W, 5¼" H
Bronze, Satin Black,
Satin White, Titanium



1648
Atlantis, Pages 423,425,427,429
6" W, 16" H
Bronze, Satin Black,
Satin White, Titanium



1649
Atlantis, Pages 422,424,426,428
9" W, 24" H
Bronze, Satin Black,
Satin White, Titanium



1650
Atlantis, Pages 423, 425
6¼" W, 10½" H
Bronze, Titanium



3610
Cambridge, Pages 181,185,188
14½" W, 18" H
Burnished Brass,
Olde Bronze, Pewter



4300OL
Casa, Page 142
5" W, 24" H
Olde Black



1830
Cascade, Page 433
8" W, 14½" H
Bronze, Satin Black,
Titanium



1832
Cascade, Page 434
8" W, 14½" H
Bronze, Titanium



1834
Cascade, Pages 432-433
8" W, 18" H
Bronze, Satin Black,
Titanium



1836
Cascade, Page 434
8" W, 18" H
Bronze, Titanium



3800BN
Cirrus, Page 99
15" W, 6½" H
Brushed Nickel



5920
Daphne, Pages 350-352
8½" W, 9" H
Brushed Bronze,
Brushed Nickel, Chrome




3282SL
Flourish, Page 97
9" W, 16½" H
Silver Leaf



FR41941PAL
Karma, Page 246
5" W, 5" H
Polished Aluminum



FR41942PAL
Karma, Page 246
17" W, 5" H
Polished Aluminum



3162OZ
Lanza, Page 101
10" W, 11½" H
Oil Rubbed Bronze



1647
Luna, Page 442
9" W, 9" H
Bronze, Satin Black,
Satin White, Titanium



1660
Luna, Page 441
6" W, 16" H
Bronze, Satin Black,
Titanium



1664
Luna, Pages 440-441
9" W, 24" H
Bronze, Satin Black,
Titanium



1666, 1667
Luna, Page 443
9" W, 5¼" H
Bronze, Satin Black,
Titanium



FR40572IRR
Middlefield, Page 297
8" W, 16½" H
Iron Rust



FR56560PCM
Mira Mesh, Page 353
6" W, 16¼" H
Polished Chrome



FR55450PCM
Mira Fizz, Page 355
6" W, 16¼" H
Polished Chrome



2150KZ
Mondrian, Page 475
7" W, 11" H
Buckeye Bronze



2154KZ
Mondrian, Page 475
9" W, 14¼" H
Buckeye Bronze

HINKLEY LIGHTING ADA COMPLIANT SCONCES

PICTORIAL INDEX



4570KZ
Mondrian, Page 107
7" W, 11" H
Buckeye Bronze



4572KZ
Mondrian, Page 107
7" W, 24" H
Buckeye Bronze



FR

FR47200PNI
Omni, Pages 241, 335
4½" W, 7" H
Polished Nickel



1908
Saturn, Pages 417, 419
7½" W, 12½" H
Metro Bronze, Stainless Steel



4900
Sussex, Page 147, 150
14" W, 14" H
Brushed Nickel, English Bronze



Fixtures shown: Zelda 3444 PN and 3440 PN, page 55

INDOOR FLUSH MOUNTS HINKLEY & FREDRICK RAMOND

PICTORIAL INDEX



RR

FR43621PNI
Alexandra, Page 261
18½" Dia., 16¼" H
Polished Nickel



5191CM
Ashley, Page 333
15¼" Dia., 7" H
Chrome



RR

FR42873VBZ
Ava, Page 301
17" Dia., 19" H
Vintage Bronze



5551
Avon, Pages 336-337
15" Dia., 7¼" H
Brushed Nickel, Brushed Bronze,
Chrome



RR

FR44104FRM
Barcelona, Page 271
23½" Dia., 13" H
French Marble



RR

FR44109FRM
Barcelona, Page 271
30½" Dia., 26¼" H
French Marble



RR

FR44501BBZ
Bentley, Page 284
16" Dia., 15" H
Brushed Bronze



RR

FR43531PNI
Bijou, Page 259
15" Dia., 12¼" H
Polished Nickel



4660
Bolla, Pages 111, 115, 119, 388-390
16¼" Dia., 8" H
Brushed Nickel, Brushed
Bronze, Olde Bronze



4651
Bolla, Pages 111, 115, 119
19¼" Dia., 14" H
Brushed Nickel, Brushed Bronze,
Olde Bronze



4669
Bolla, Pages 111, 115, 119
23¾" Dia., 16" H
Brushed Nickel, Brushed Bronze,
Olde Bronze



4631
Brantley, Pages 123, 125,
127, 369, 383
17" Dia., 7" H
Brushed Nickel,
Oil Rubbed Bronze,
Textured Black



4632
Brantley, Pages 123, 125, 127
17" Dia., 10¼" H
Brushed Nickel, Oil Rubbed Bronze,
Textured Black



RR

FR41431PAL
Broadway, Page 253
8" W, 8½" H
Polished Aluminum



3612
Cambridge, Page 182, 185, 188
14½" Dia., 13" H
Burnished Brass,
Olde Bronze, Pewter



3616
Cambridge, Page 182, 185, 188
16¾" Dia., 7¾" H
Burnished Brass,
Olde Bronze, Pewter



RR

FR42341PCM
Cameron, Page 293
18" Dia., 14" H
Polished Chrome



4771SL
Carlton, Page 207
24" Dia., 17½" H
Silver Leaf



RR

FR44621BCH
Carabel, Page 275
14¾" Dia., 14" H
Brushed Champagne



RR

FR44622BCH
Carabel, Page 274
20½" Dia., 15" H
Brushed Champagne



3501OL
Casa, Pages 143, 394
14¼" Dia., 8¾" H
Olde Black



4011OL
Casa, Page 143
13" Dia., 12" H
Olde Black



4311OL
Casa, Page 143
23" Dia., 14" H
Olde Black



RR

FR43751SLF
Caspia, Page 269
16" Dia., 9½" H
Silver Leaf



3804BN
Cirrus, Page 99
20" W, 12" H
Brushed Nickel



3805BN
Cirrus, Page 99
28" W, 12" H
Brushed Nickel



4561AT
Cello, Page 163
19" Dia., 16" H
Antique Bronze



3140
Congress, Page 218
8" Dia., 9½" H
Antique Nickel,
Brushed Caramel, Chrome,
Oil Rubbed Bronze



3141
Congress, Page 218
12" Dia., 11¾" H
Antique Nickel,
Brushed Caramel, Chrome,
Oil Rubbed Bronze



3143
Congress, Page 219
7" Dia., 11¾" H
Antique Nickel,
Brushed Caramel, Chrome,
Oil Rubbed Bronze

HINKLEY & FREDRICK RAMOND INDOOR FLUSH MOUNTS

PICTORIAL INDEX



3144
Congress, Page 219
8 3/4" Dia., 11" H
Antique Nickel, Brushed Caramel,
Chrome, Oil Rubbed Bronze



3145
Congress, Page 219
6" Dia., 12" H
Antique Nickel, Brushed Caramel,
Chrome, Oil Rubbed Bronze



3146
Congress, Page 218
8" Dia., 9 1/2" H
Antique Nickel, Brushed Caramel,
Chrome, Oil Rubbed Bronze



3147
Congress, Page 218
12" Dia., 11 1/4" H
Antique Nickel, Brushed Caramel,
Chrome, Oil Rubbed Bronze



3148
Congress, Page 222
10 3/4" Dia., 9 3/4" H
Antique Nickel, Brushed Caramel,
Chrome, Oil Rubbed Bronze



3149
Congress, Page 219
7" Dia., 11 1/4" H
Antique Nickel, Brushed Caramel,
Chrome, Oil Rubbed Bronze



3150
Congress, Page 219
8 3/4" Dia., 11" H
Antique Nickel, Brushed Caramel,
Chrome, Oil Rubbed Bronze



3151
Congress, Page 219
6" Dia., 12" H
Antique Nickel, Brushed Caramel,
Chrome, Oil Rubbed Bronze



3961PL
Darlen, Page 81
16" Dia., 11 1/4" H
Polished Antique Nickel



3661BN
Dillon, Page 83
15" Dia., 7 3/4" H
Brushed Nickel



3662BN
Dillon, Page 83
18 1/4" Dia., 11" H
Brushed Nickel



4591RY
Dunhill, Page 153
16" Dia., 13" H
Royal Bronze



3281SL
Flourish, Page 97
15" Square, 13 1/2" H
Silver Leaf



3472
Gentry, Pages 177, 179
9 1/2" Dia., 9 1/2" H
Pewter, Polished Brass



3473
Gentry, Pages 177, 179
11 1/2" Dia., 9 1/2" H
Pewter, Polished Brass



3301
Hadley, Pages 232-233
14" Dia., 5 1/2" H
Antique Nickel, Brushed Bronze,
Chrome, Oil Rubbed Bronze



3302
Hadley, Pages 232-233
12" Dia., 4 3/4" H
Antique Nickel, Brushed Bronze,
Chrome, Oil Rubbed Bronze



3304
Hadley, Pages 232-233
20" Dia., 7 3/4" H
Antique Nickel, Brushed Bronze,
Chrome, Oil Rubbed Bronze



3200
Hampton, Pages 91, 94
15" Dia., 11 3/4" H
Antique Nickel,
Brushed Bronze



3201
Hampton, Pages 91, 94
20" Dia., 12" H
Antique Nickel,
Brushed Bronze



3211
Hampton, Pages 91, 94
26" Dia., 14 1/2" H
Antique Nickel,
Brushed Bronze



3641
Harper, Pages 226-227
14 1/2" Dia., 10" H
Brushed Nickel, Chrome,
Oil Rubbed Bronze



3220
Hathaway, Page 103
16" Dia., 11 1/4" H
Antique Nickel,
Olde Bronze



3221
Hathaway, Page 103
20 3/4" Dia., 12 1/4" H
Antique Nickel,
Olde Bronze



3321
Hutton, Pages 230-231
16 1/2" Dia., 10" H
Brushed Nickel, Chrome,
Oil Rubbed Bronze



FR36501
Ion, Page 249
21" Dia., 11" H
Anodized Black, Anodized Gold,
Anodized Silver



5391
Isabella, Pages 396-397
15" Dia., 9 3/4" H
Burnished Brass,
Polished Antique Nickel



53241BN
Jules, Page 360
15" Dia., 8 3/4" H
Brushed Nickel



FR41943PAL
Karma, Page 246
18 1/2" W, 5" H
Polished Aluminum



FR41947PAL
Karma, Page 245
18 3/4" W, 5" H
Polished Aluminum

INDOOR FLUSH MOUNTS HINKLEY & FREDRICK RAMOND

PICTORIAL INDEX



FR42721SLF
Kingsley, Page 283
16" Dia., 15½" H
Silver Leaf



3161OZ
Lanza, Page 101
15¼" Square, 10½" H
Oil Rubbed Bronze



4061VZ
Lauren, Page 137
20¼" Dia., 10½" H
Victorian Bronze



4161OB
Mayflower, Page 157
15" Dia., 12" H
Olde Bronze



3871
Meridian, Pages 65, 69, 366-368
16" Dia., 12¼" H
Brushed Nickel, Chrome,
Satin Black



4971BN
Midtown, Page 71
18" Dia., 11¼" H
Brushed Nickel



FR45601
Mime, Pages 263, 265
17½" Dia., 22" H
Brushed Nickel, French Bronze



4571KZ
Mondrian, Page 107
16" W, 12" H
Buckeye Bronze



FR41611ORB
Nest, Page 291
16½" Dia., 9½" H
Oil Rubbed Bronze



FR41621ORB
Nest, Page 291
8" Dia., 12" H
Oil Rubbed Bronze



FR41622ORB
Nest, Page 291
20" Dia., 11½" H
Oil Rubbed Bronze



5421
Ocho, Page 342, 330-332
17" Dia., 7" H
Brushed Nickel,
Brushed Bronze, Chrome



FR47201PNI
Omni, Page 241
16" W, 11¼" H
Polished Nickel



FR42401BRC
Pandora, Page 288
14" Dia., 11½" H
Brushed Cinnamon



4431KZ
Parker, Page 129
16" Dia., 12¼" H
Buckeye Bronze



3821
Pelham, Pages 228-229
18¾" W, 13¾" H
Brushed Nickel, Brushed Bronze,
Chrome, Oil Rubbed Bronze



5251
Pinnacle, Page 338-339
16¼" Dia., 7¼" H
Antique Nickel, Chrome



4102
Plantation, Pages 197, 200, 203,
400-401, 12" Dia., 8" H
Burnished Brass, Copper Bronze,
Polished Antique Nickel,
Pearl Bronze



4881
Plantation, Pages 197, 200, 203,
400-401, 16" Dia., 8¾" H
Burnished Brass, Copper Bronze,
Polished Antique Nickel,
Pearl Bronze



4241OB
Plymouth, Pages 160, 391
17½" Dia., 8¾" H
Olde Bronze



4242OB
Plymouth, Page 160
16" Dia., 12¼" H
Olde Bronze



4071BN
Princeton, Page 63
17" Dia., 12¼" H
Brushed Nickel



FR49432RCO
Prosecco, Page 257
17" Dia., 19" H
Renaissance Copper



3712FB
Rockford, Page 191
14¼" Dia., 12¼" H
Forum Bronze



3716FB
Rockford, Page 191
16¼" Dia., 7¼" H
Forum Bronze



4541RB
Sloan, Page 145
16" Dia., 10½" H
Regency Bronze



4543RB
Sloan, Page 145
24" Dia., 14" H
Regency Bronze



4721MC
Stowe, Pages 135, 392
15½" Dia., 6¾" H
Metro Copper



4791
Sussex, Pages 148, 151
16" Dia., 15" H
Brushed Nickel, English Bronze



4170VZ
Thistledown, Page 132
15" Dia., 13" H
Victorian Bronze

HINKLEY & FREDRICK RAMOND INDOOR FLUSH MOUNTS

PICTORIAL INDEX



4171VZ
Thistledown, Pages 132, 559
15½" Dia., 8" H
Victorian Bronze



4021AN
Truman, Page 155
16" Dia., 12" H
Antique Nickel



4701
Valley, Pages 87, 89
18½" Dia., 12¼" H
Brushed Nickel, Vintage Black



4702
Valley, Pages 87, 89
23" Dia., 13¾" H
Brushed Nickel, Vintage Black



4801SU
Veranda, Page 209
20" Dia., 16" H
Summerstone



4611BN
Whitney, Page 121
15" Dia., 16½" H
Brushed Nickel



3001
Wingate, Page 171, 174
16" W, 15¼" H
Oil Rubbed Bronze,
Polished Antique Nickel



3003
Wingate, Page 171, 174
12" W, 13" H
Oil Rubbed Bronze,
Polished Antique Nickel



FR43359PSS
Xanadu, Page 255
14¾" Dia., 16" H
Polished Stainless Steel



3441
Zelda, Pages 55, 57
14¾" W, 12½" H
Polished Nickel,
Vintage Brass

HINKLEY & FREDRICK RAMOND PENDANTS

PICTORIAL INDEX



3124
Amelia, Pages 211-212
12¾" Dia.
46¾" H Max.
Chrome, Buckeye
Bronze, Polished
Antique Nickel



3127
Amelia, Pages 211-212
11½" Dia.
42¾" H Max.
Chrome, Buckeye
Bronze, Polished
Antique Nickel



2302KZ
Aria, Page 451
5" Dia.
51½" H Max.
Buckeye Bronze



4667
Bolla, Pages 109,
113, 117
7¾" Dia.
39¾" H Max.
Brushed Nickel,
Brushed Bronze,
Olde Bronze



4661
Bolla, Pages 110,
114, 118
15½" Dia.
48" H Max.
Brushed Nickel,
Brushed Bronze,
Olde Bronze



4637
Brantley, Pages 123,
125, 127
4¾" Dia.
41¼" H Max.
Brushed Nickel,
Oil Rubbed Bronze,
Textured Black




FR41436PAL
Broadway, Page 253
8" W
52¾" H Max.
Polished Aluminum

PENDANTS HINKLEY & FREDRICK RAMOND

PICTORIAL INDEX



FR



FR



FR



FR41437PAL
Broadway, Page 253
8" W
47½" H Max.
Polished Aluminum

FR41439PAL
Broadway, Page 253
9" W
113" H Max.
Polished Aluminum

FR42347PCM
Cameron, Page 293
8" Dia.
44¾" H Max.
Polished Chrome

4017OL
Casa, Page 143
5½" Dia.
45" H Max.
Olde Black

4567AT
Cello, Page 163
8½" Dia.
40¾" H Max.
Antique Bronze

3128
Congress, Page 216
7" Dia.
39½" H Max.
Antique Nickel,
Brushed Caramel,
Chrome,
Oil Rubbed Bronze

3129
Congress, Pages 216, 217
8¾" Dia.
41½" H Max.
Antique Nickel,
Brushed Caramel,
Chrome,
Oil Rubbed Bronze



3130
Congress, Page 215
8" Dia.
39½" H Max.
Antique Nickel,
Brushed Caramel,
Chrome,
Oil Rubbed Bronze

3131
Congress, Page 214
12" Dia.
42¾" H Max.
Antique Nickel,
Brushed Caramel,
Chrome,
Oil Rubbed Bronze

3133
Congress, Page 216
7" Dia.
41¾" H Max.
Antique Nickel,
Brushed Caramel,
Chrome,
Oil Rubbed Bronze

3134
Congress, Page 216, 217
8¾" Dia.
41½" H Max.
Antique Nickel,
Brushed Caramel,
Chrome,
Oil Rubbed Bronze

3135
Congress, Page 217
6" Dia.
42½" H Max.
Antique Nickel,
Brushed Caramel,
Chrome,
Oil Rubbed Bronze

3136
Congress, Page 215
8" Dia.
35½" H Max.
Antique Nickel,
Brushed Caramel,
Chrome,
Oil Rubbed Bronze

3137
Congress, Page 214
12" Dia.
42¾" H Max.
Antique Nickel,
Brushed Caramel,
Chrome,
Oil Rubbed Bronze

HINKLEY & FREDRICK RAMOND PENDANTS

PICTORIAL INDEX



3138
Congress, Page 222
9½" Dia.
41" H Max.
Antique Nickel,
Brushed Caramel,
Chrome,
Oil Rubbed Bronze



3139
Congress, Page 217
6" Dia.
42½" H Max.
Antique Nickel,
Brushed Caramel,
Chrome,
Oil Rubbed Bronze



4097RI
Cordillera, Page 105
7½" Dia.
55½" H Max.
Rustic Iron



3667BN
Dillon, Page 83
6" Dia.
40" H Max.
Brushed Nickel



2192
Dorian, Pages 446-447
6" W
18¼" H Max.
Bronze, Titanium



FR38510
Globe, Page 312
10" Dia.
103" H Max.
Brushed Nickel, Cloud,
Polished Chrome



3207
Hampton, Pages 92, 95
7" Dia.
44" H Max.
Antique Nickel,
Brushed Bronze




3017BN
Landon, Page 169
8" Dia.
48" H Max.
Brushed Nickel



4067VZ
Lauren, Page 137
7¾" Dia.
47¼" H Max.
Victorian Bronze




FR35002
FR35003
FR35004
Loft, Pages 308-309
4" W, 88" H Max.
Maple with
Brushed Nickel,
Chrome or
Bronze



FR35007
FR35008
FR35009
Loft, Page 309
4" W, 81½" H Max.
Maple with
Brushed Nickel,
Chrome or
Bronze



FR35012
FR35013
FR35014
Loft, Pages 308-309
4" W, 88" H Max.
Walnut with
Brushed Nickel,
Chrome or
Bronze




FR35017
FR35018
FR35019
Loft, Page 309
4" W, 81½" H Max.
Walnut with
Brushed Nickel,
Chrome or
Bronze




FR35022
FR35023
FR35024
Loft, Pages 308-309
6" W, 88" H Max.
Cherry with
Brushed Nickel,
Chrome or
Bronze

PENDANTS HINKLEY & FREDRICK RAMOND

PICTORIAL INDEX



FR35027
FR35028
FR35029
Loft, Page 309
6" Dia., 81" H Max.
Cherry with
Brushed Nickel,
Chrome or
Bronze



FR31557
Luxe, Pages 316-317
6" W
40½" H Max.
Brushed Nickel,
Polished Chrome,
Vintage Bronze



3587
Margeaux, Pages 59, 61
3½" W
47½" H Max.
Polished Nickel,
Vintage Brass




4151OB
Mayflower, Page 157
14" Dia.
42½" H Max.
Olde Bronze



4167OB
Mayflower, Page 157
5" Dia.
41¾" H Max.
Olde Bronze



3877
Meridian, Pages 65, 69
7½" Dia.
36¾" H Max.
Brushed Nickel,
Satin Black



FR45607
Mime, Pages 263, 265
9" W
39½" H Max.
Brushed Nickel,
French Bronze



4577KZ
Mondrian, Page 107
7" W
43½" H Max.
Buckeye Bronze



FR41617ORB
Nest, Page 290
8" Dia.
53½" H Max.
Oil Rubbed Bronze



FR41627ORB
Nest, Page 291
6" Dia.
41" H Max.
Oil Rubbed Bronze



FR42407BRC
Pandora, Page 288
9½" Dia.
45½" H Max.
Brushed Cinnamon



4437KZ
Parker, Page 129
4¾" Dia.
46½" H Max.
Buckeye Bronze



5317
Plantation, Pages 197,
199, 202
5" Dia.
40¾" H Max.
Burnished Brass,
Polished Antique Nickel,
Pearl Bronze



4247OB
Plymouth, Page 159
6½" Dia.
43" H Max.
Olde Bronze



1322
Shelter, Pages 453,
455, 457
6¾" Dia.
54" H Max.
Black, Buckeye Bronze,
Hematite




1328
Shelter, Page 455
8¾" Dia.
57" H Max.
Black



4547RB
Sloan, Page 145
6" Dia.
50" H Max.
Regency Bronze



4727MC
Stowe, Page 135
5" Dia.
43¾" H Max.
Metro Copper



FR30407
Stratus, Page 313
6¾" W
110" H Max.
Brushed Aluminum
and Brushed Bronze,
Brushed Nickel, Polished
and Brushed Aluminum,
Polished Nickel



FR33507
Vivo, Pages 314-315
7½" W
33½" H Max.
Brushed Nickel,
Cloud,
Polished Chrome



4717RB
Tahoe
7" Dia.
39½" H Max.
Royal Bronze



4177VZ
Thistledown, Page 131
5¼" Dia.
43½" H Max.
Victorian Bronze



4027AN
Truman, Page 155
5¼" Dia.
41¾" H Max.
Antique Nickel



4707
Valley, Page 87, 89
5¼" Dia.
45¼" H Max.
Brushed Nickel,
Vintage Black



FR46207BAM
Zen, Page 305
4" W, 4" D
82½" H Max.
Bamboo



FR46208BAM
Zen, Page 305
4" W, 4" D
78½" H Max.
Bamboo



3447
Zelda, Pages 55, 57
4¾" Dia.
44¾" H Max.
Polished Nickel,
Vintage Brass

BATH HINKLEY LIGHTING

PICTORIAL INDEX



ABBIE
Page 378
Brushed Caramel



ABBIE
Page 377
Brushed Nickel



ABBIE
Page 376
Chrome



ADELE
Page 340
Brushed Nickel



ALICE
Page 374
Antique Nickel



ALICE
Page 375
Brushed Bronze



ANNA
Page 348
Chrome



ASHBURY
Page 343
Chrome



ASHLEY
Page 333
Chrome



AVON
Page 337
Brushed Nickel



AVON
Page 336
Chrome



BOLLA
Page 389
Brushed Bronze



BOLLA
Page 388
Brushed Nickel



BOLLA
Page 390
Olde Bronze



BRANTLEY
Page 383
Brushed Nickel



BROOKE
Page 386
Antique Nickel



CASA
Page 394
Olde Black



DAPHNE
Page 351
Brushed Nickel



DAPHNE
Page 352
Brushed Bronze



DAPHNE
Page 350
Chrome



DARIA
Page 356
Chrome



DUET
Page 357
Brushed Nickel



ELEMENT
Page 365
Brushed Nickel



ENVY
Page 347
Brushed Nickel



ENVY
Page 346
Chrome



FLYNN
Page 395
Blacksmith



FRANCOISE
Page 399
Burnished Brass



FRANCOISE
Page 398
Polished Antique Nickel



ISABELLA
Page 397
Burnished Brass



ISABELLA
Page 396
Polished Antique Nickel



JORDAN
Page 370
Brushed Nickel



JOSIE
Page 341
Brushed Nickel



JULES
Page 360
Brushed Nickel



KATIA
Page 334
Chrome



LANZA
Page 372
Antique Nickel



LANZA
Page 373
Brushed Bronze



LATITUDE
Page 361
Brushed Nickel



LOLA
Page 362
Brushed Nickel



MASON
Page 369
Textured Black



MERIDIAN
Page 367
Brushed Nickel



MERIDIAN
Page 366
Chrome



MERIDIAN
Page 368
Satin Black



MIA
Page 371
Brushed Nickel



MILEY
Page 332
Brushed Caramel



MILEY
Page 331
Brushed Nickel



MILEY
Page 330
Chrome



MIRA FIZZ
Page 355
Polished Chrome



MIRA MESH
Page 353
Polished Chrome



NEST
Page 393
Oil Rubbed Bronze



OCHO
Page 342
Chrome

BATH HINKLEY LIGHTING

PICTORIAL INDEX



OMNI
Page 335
Polished Nickel



PINNACLE
Page 339
Antique Nickel



PINNACLE
Page 338
Chrome



PLANTATION
Pages 401
Burnished Brass



PLANTATION
Pages 400
Polished Antique Nickel



PLYMOUTH
Page 391
Olde Bronze



REESE
Page 387
Antique Nickel




SAN SIMEON
Pages 402
Silver Leaf



SHELLY
Page 381
Brushed Nickel



SHELLY
Page 380
Chrome



SOPHIE
Page 364
Brushed Nickel



STOWE
Page 392
Metro Copper



TAYLOR
Page 345
Brushed Nickel



TAYLOR
Page 344
Chrome



TORY
Page 382
Brushed Nickel



WINTON
Page 359
Brushed Nickel



WINTON
Page 358
Chrome



YORKTOWN
Page 384
Antique Nickel



YORKTOWN
Page 385
Brushed Bronze



ZARA
Page 349
Chrome



ZINA
Page 363
Brushed Nickel



ARIA
Pages 450-451
Buckeye Bronze



ATLANTIS
Pages 422-423
Bronze



ATLANTIS
Pages 428-429
Satin Black



ATLANTIS
Pages 426-427
Satin White



ATLANTIS
Pages 424-425
Titanium



AUGUSTA
Pages 578-579
Copper Bronze



AURORA
Pages 490-491
Metro Bronze



BARRINGTON
Pages 570-571
Victorian Bronze



BINGHAM
Pages 518-519
Sienna



BOLLA
Pages 488-489
Black



BOLLA
Pages 486-487
Olde Bronze



BRIGHTON
Pages 508-509
Sienna



BRYNMAR
Pages 598-599
Regency Bronze



CAMELOT
Pages 532-533
Black



CAPE COD
Pages 494-495
Sienna Bronze



CASA
Pages 554-555
Olde Black



CASCADE
Pages 432-435
Bronze



CASCADE
Pages 432-435
Satin Black



CASCADE
Pages 432-435
Titanium



CASTELLE
Pages 482-483
Black



CASTELLE
Pages 484-485
Bronze



CEDAR HILL
Page 541
Black



CEDAR HILL
Page 540
Oil Rubbed Bronze



CHERRY CREEK
Pages 546-547
Oil Rubbed Bronze



CHERRY CREEK
Pages 544-545
Vintage Black



CHESTERFIELD
Pages 564-565
Black



CLIFTON BEACH
Pages 594-595
Antique Copper



CLIFTON PARK
Pages 596-597
Copper Bronze



CORDILLERA
Pages 556-557
Buckeye Bronze



DISTRICT
Pages 420-421
Bronze

OUTDOOR HINKLEY LIGHTING



DISTRICT
Pages 420-421
Titanium



DORIAN
Page 447
Bronze



DORIAN
Page 446
Titanium



EDGEWATER
Pages 530-531
Black



ELM
Pages 552-553
Regency Bronze



FORUM
Pages 584-585
French Bronze



FORUM
Pages 586-587
Museum Black



FREEPORT
Page 466
Black



FREEPORT
Pages 464-465
Oil Rubbed Bronze



FREEPORT
Page 467
Old Penny



GRAYSON
Page 492
Autumn



GRAYSON
Page 493
Charcoal



HARBOR
Pages 470-471
Anchor Bronze



HARBOR
Pages 472-473
Satin Black



HARBOR
Pages 468-469
Titanium



HOLBROOK
Pages 550-551
Black



KEY WEST
Pages 574-575
Regency Bronze



KUBE
Pages 436-439
Bronze



KUBE
Pages 436-439
Satin Black



KUBE
Pages 436-439
Satin White



KUBE
Pages 436-439
Titanium



LEDGEWOOD
Pages 480-481
Museum Bronze



LEDGEWOOD
Pages 478-479
Vintage Black



LIBERTY
Page 502
Sienna



LIBERTY
Page 503
Victorian Bronze



LUCERNE
Pages 576-577
Copper Bronze



LUNA
Pages 440-443
Bronze



LUNA
Pages 440-443
Satin Black



LUNA
Pages 440-443
Titanium



MANHATTAN
Pages 476-477
Olde Bronze





MANOR HOUSE
Pages 528-529
Black



MONDRIAN
Page 475
Buckeye Bronze



MONTAUK
Pages 504-505
Sienna



MONTICELLO
Pages 592-593
Copper Bronze



MONTREAL
Pages 606-607
Aged Iron



NANTUCKET
Pages 506-507
Aged Brass



NEW CASTLE
Pages 496-497
Black



OXFORD
Pages 572-573
Midnight Bronze



PEMBROKE
Pages 462-463
Spanish Bronze



PLANTATION
Pages 610-612
Copper Bronze



PLANTATION
Pages 608-609
Pearl Bronze



PUTNEY BRIDGE
Pages 512-513
Black



RALEY
Pages 526-527
Museum Black



RANDOLPH
Pages 536-537
Autumn



RANDOLPH
Pages 538-539
Black



REEF
Page 461
Victorian Bronze



REEF
Page 460
Hematite



REGAL
Pages 534-535
Black Granite



REVERE
Pages 516-517
Sienna



RICHMOND
Pages 524-525
Museum Black



ROWE PARK
Pages 602-603
Oil Rubbed Bronze



ROWE PARK
Pages 600-601
Pearl Bronze



SAN CLEMENTE
Pages 588-589
Copper Bronze



SAN CLEMENTE
Pages 590-591
Museum Black



SATURN
Pages 418-419
Metro Bronze



SATURN
Pages 416-417
Stainless Steel



SEDGWICK
Pages 514-515
Sienna



SENATOR
Page 523
Black



SHELTER
Pages 454-455
Black



SHELTER
Pages 456-457
Buckeye Bronze

OUTDOOR HINKLEY LIGHTING



SHELTER
Pages 452-453
Hematite



SIERRA
Page 474
Spanish Bronze



SOLARA
Page 449
Bronze



SOLARA
Page 448
Titanium



SORRENTO
Pages 604-605
Aged Iron



STRATFORD
Page 543
Museum Black



STRATFORD
Page 542
Oil Rubbed Bronze



SULLIVAN
Page 459
Black



SULLIVAN
Page 458
Hematite



SURF
Pages 414-415
Bronze



SURF
Pages 414-415
Stainless Steel



TAHOE
Pages 548-549
Regency Bronze



THISTLEDOWN
Pages 558-559
Victorian Bronze



TITAN
Pages 444-445
Buckeye Bronze



TITAN
Pages 444-445
Hematite



TITAN
Pages 444-445
Titanium



TRAFALGAR
Page 562
Mocha



TRAFALGAR
Page 563
Museum Black



TRELIS
Pages 566-568
Regency Bronze



VALLEY FORGE
Pages 510-511
Sienna



WABASH
Page 560
Mocha



WABASH
Page 561
Museum Black



WESTWINDS
Pages 498-499
Sienna



WINDSOR
Pages 582-583
Black



WINDSOR
Pages 580-581
River Rock



YORK
Pages 520-521
Black

HINKLEY LIGHTING OUTDOOR FLUSH MOUNTS



2633
Bolla, Pages 487, 489
16 3/4" Dia., 8" H
Black, Olde Bronze



1712BK
Camelot, Page 533
11 1/4" Dia., 9 1/4" H
Black



2203SZ
Cape Cod, Page 495
7" Dia., 9 3/4" H
Sienna Bronze



1273
Cherry Creek, Pages 545, 547
12" W, 7 1/4" H
Oil Rubbed Bronze,
Vintage Black



2429CB
Clifton Park, Page 596
12 1/2" Dia., 6 3/4" H
Copper Bronze



1683BK
Edgewater, Page 531
13" Dia., 9" H
Black



2573
Harbor, Pages 469, 471, 473
12 1/4" W, 7" H
Anchor Bronze, Satin Black,
Titanium



1613RB
Key West, Page 575
15" Dia., 8 1/4" H



1763
Kube, Page 438
6" W, 6 1/4" H
Bronze, Satin Black,
Satin White, Titanium



2313CB
Lucerne, Page 577
12 1/2" Dia., 7 1/4" H
Copper Bronze



1663
Luna, Page 442
8" W, 7 1/4" H
Bronze, Satin Black, Titanium



1243MN
Oxford, Page 573
16 1/4" Dia., 7 1/2" H
Midnight Bronze



2123PZ
Plantation, Page 609
16" Dia., 8 3/4" H
Pearl Bronze



2128PZ
Plantation, Page 609
12" Dia., 8" H
Pearl Bronze



4102
Plantation, Pages 197, 200,
203, 400-401, 612
12" Dia., 8" H
Burnished Brass, Copper
Bronze, Pearl Bronze,
Polished Antique Nickel



4881
Plantation, Pages 197, 200,
203, 400-401, 612
16" Dia., 8 3/4" H
Burnished Brass, Copper
Bronze, Pearl Bronze,
Polished Antique Nickel



1713BG
Regal, Page 535
11 3/4" Dia., 9" H
Black Granite



2443CB
San Clemente, Page 579,
589, 591, 593
15 1/4" Dia., 9" H
Copper Bronze, Museum Black



2243RB
Tahoe, Page 549
9 1/2" W, 6" H
Regency Bronze



4171VZ
Thistledown, Pages 132, 559
15 1/4" Dia., 8" H
Victorian Bronze



2999SN
Westwinds, Page 499
13 1/2" Dia., 7 1/2" H
Sienna

As part of our 'Life Aglow' campaign, Hinkley interviewed acclaimed interior designers, editors, stylists and bloggers to bring you invaluable ideas on selecting the right lighting. Look for their insider secrets that offer informative and entertaining recommendations throughout Hinkley's Design Centers in this catalog and on hinkleylighting.com. For full bios on each contributor, visit hinkleylighting.com.



MONA ROSS BERMAN INTERIORS
PHILADELPHIA, PA
MONAROSSBERMAN.COM



ROB & JILL BRINSON JILL SHARP STYLE
ATLANTA, GA
JILLSHARPSTYLE.COM



AMY ELBERT SENIOR ARCHITECTURE EDITOR
TRADITIONAL HOME
TRADITIONALHOME.COM



CHRISTINA FLUEGGE GREIGE DESIGN
SAN JOSE, CA
GREIGEDESIGN.COM



JAMIE HERZLINGER INTERIORS
NEW YORK CITY & SCOTTSDALE, AZ
JAMIEHERZLINGER.COM



TAMARA KAYE-HONEY HOUSE OF HONEY
LOS ANGELES
HOUSEOFHONEY.LA



RYAN KORBAN
NEW YORK CITY
RYANKORBAN.COM



LISA MCDENNON DESIGN
LAGUNA BEACH, CA
LISAMCDENNONDESIGN.COM




SARAH SWANSON DESIGN
CALGARY, ALBERTA, CANADA
SARAHSWANSONDESIGN.COM



CHANDELIER COLLECTIONS

AMELIA	211
BOLLA	108
BRANTLEY	122
CAMBRIDGE	180
CARLTON	206
CASA	140
CELLO	162
CHANNING	078
CIRRUS	098
CONGRESS	214
CORDILLERA	104
DARIEN	080
DILLON	082
DUNHILL	152
FLOURISH	096
GENTRY	176
HADLEY	232
HAMPTON	090
HARLOW	050
HARPER	226
HATHAWAY	102
HUTTON	230
LANDON	168
LANZA	100
LAUREN	136
MARCELLINA	204
MARGEAUX	058
MARION	138
MAYFLOWER	156
MERIDIAN	064
MIDTOWN	070
MONACO	074
MONDRIAN	106
PARKER	128
PELHAM	228
PIPER	072
PLANTATION	196
PLYMOUTH	158
PRINCETON	062
ROCKFORD	190
SLOAN	144
SPLENDOR	048
STOWE	134
SUSSEX	146
THISTLEDOWN	130
TRUMAN	154
VALLEY	086
VERANDA	208
VICTORY	084
VIRGINIAN	192
WHITNEY	120
WINGATE	170
YORKTOWN	164
ZELDA	054

CHANDELIERS



"There are so many important considerations to take in to account when selecting a chandelier – style, scale, how much light do you need it to emit – to name a few. But I always start with those factors so I know we are zeroing in on what will work from the get-go. After that, I cast a pretty wide net in terms of options. I like to keep an open mind because you never know when you'll see something that just makes sense and really enhances the room."

MONA ROSS BERMAN
MONA ROSS BERMAN INTERIORS
PHILADELPHIA, PA

BIG TIME RUSH

THE PERFECT CHANDELIER

will completely elevate the perception of a space. Whether you prefer contemporary or traditional decor, selecting the right chandelier will set the tone and, if you want, create a jaw-dropping effect. It can improve even the most basic spaces or add a deeper layer of luxury to already well-designed areas. Invest in researching the wide variety of designs, materials and sizes available to find the ultimate chandelier that completes your dream room.

Fixtures shown on page 39: Carlton 4775 SL, page 207
Fixture shown here: Fredrick Ramond's Caspia FR43/59SLF, page 268

FIND YOUR FIT It's important to remember that just like anything else, a chandelier should represent your own personal style. Don't get caught up in "playing by the rules." Pick something that can enhance your space and works with the way you actually live.



1.

"A chandelier can be the crowning jewel of the room! The perfect chandelier will tie all of the elements of the room together. You can capture so many styles with the perfect chandelier!"

SARAH SWANSON
SARAH SWANSON DESIGN
CALGARY, ALBERTA
CANADA



2.

There are several key features to look for when selecting your perfect chandelier: **DESIGN, SCALE, FINISH AND MATERIALS.** Once you've identified your basic lighting needs and decided where you want to hang the fixture, take time to research various styles and find a chandelier that complements your unique decor. From there, ensure you choose the right size (see p. 46) and finish so it complements the overall space. Interesting materials incorporated into the design, from wood to crystal details, can add another layer of stylish sophistication.

3.



"Lighting is a key element to me in my own home and in all of my projects. I consider the main light fixtures before I even begin to look for the furniture. I consider lighting as important as the flooring, which is where I usually begin the design process!"

JAMIE HERZLINGER
JAMIE HERZLINGER INTERIORS
NEW YORK CITY & SCOTTSDALE, AZ



"GET BY WITH A LITTLE HELP FROM A FRIEND"

Visiting a local showroom will allow you to view fixtures first hand, get comfortable with their quality and allow you to work with an expert. Visit hinkleylighting.com to find a showroom in your area.

"I love to group fixtures, and if there are multiple sizes or shapes you can create an amazing one-of-a-kind installation. This application is very successful with high ceilings and in larger living spaces such as a great room."

LISA McDENNON
LISA McDENNON DESIGN
LAGUNA BEACH, CA

GET YOUR GROUP ON

SOMETIMES MORE IS MORE! MAKE THE "WOW" FACTOR HAPPEN BY GROUPING TOGETHER CHANDELIERS OR PENDANTS FOR A STRIKING STYLE STATEMENT. CONSIDER THE DESIGN AND SIZE OF THE FIXTURE CAREFULLY, AS WELL AS WHETHER THE SPACE CAN HANDLE A LINEAR ARRANGEMENT (SUCH AS OVER A KITCHEN ISLAND) OR A MORE WHIMSICAL GROUPING THAT INCORPORATES DIFFERENT HEIGHT LEVELS.

IT ALL COMES TOGETHER when you dazzle them with details that take your lighting from average to outstanding. Enhance your lighting's creative statement by choosing unique bulbs or selecting a distinctive finish that adds another layer of personality and pizzazz.

FLIP THE SWITCH

No longer tucked away beneath shades or glass, unique bulbs can be an important design detail. From retro-chic Edisons to petite flame tip candelabras to round, modern vanity shapes, a distinctive bulb encourages customization of both the design and light level. Installing a dimmer increases your ability to manage a fixture's lighting impact on the space and, as an added benefit, gives you the option to consume less electricity and save money!



Fixtures shown: Dunhill 4598 RX, page 153, Luna 1647 SW, page 442

"Sometimes it's something as little as taking the shades off a hanging fixture that will change an entire room. Decisions that seem so small can often have a large impact. It's the details that will make your space individual."

RYAN KORBAN, RYAN KORBAN
NEW YORK CITY

"I love playing around with unexpected bulbs, they can really make a huge impact on the vibe of a chandelier."

JILL BRINSON, JILL SHARP STYLE
ATLANTA, GA

"The attribute I look for in a finish is that of excellence of quality and workmanship. Favorite finish? I love them all!"

JAMIE HERZLINGER, JAMIE HERZLINGER INTERIORS
NEW YORK CITY & SCOTTSDALE, AZ

FINISH LINE

A flattering finish has a powerful effect on the design of a fixture, emphasizing its construction and often reinforcing your overall design aesthetic. Whether your style is classic or contemporary, a finish can influence the feel of an entire room so take the overall color scheme and any other fixture or appliances into consideration. Hinkley offers an extensive array of high quality finish options to ensure there is something for everyone. If you're having trouble deciding what finish is right for a space, visit your local showroom and have an expert guide you through all of the unique options available.



Fixture shown: Fredrick Ramond's Xanadu FR43352PSS, page 255

"As a designer I am always looking to find the perfect size fixtures in just the right finish. I always love it when I can find a fixture I love and it comes in multiple sizes and finishes. Nothing is worse than finding a light fixture you love but it's not available in the correct size or color for your project!"

LISA McDENNON, LISA McDENNON DESIGN
LAGUNA BEACH, CA

COASTAL LIVING

STYLE GUIDE CHANDELIER

Make a splash with classic nautical colors and organic elements for high seas style. Anchors aweigh!

Evoke the good life with a perfect blend of beach-chic style:

- WHITE SLIPCOVERS
- SOFT LINENS
- CLASSIC FIXTURES
- SEA GRASS OR SISAL
- TEXTURED BASKETS
- ROPE DETAILING
- POPS OF BLUE
- SHELLS & STARFISH

OUR LIGHTING SUGGESTIONS:

1. HATHAWAY Chandelier Collection
3224 AN, pages 102-103
Additional finishes available.

2. HAMPTON Chandelier Collection
3211 AN, Pages 90-95
Additional finishes available.

3. SPECTRA Chandelier Collection
(Fredrick Ramond)
FR37554CLD, Pages 310-311
Additional finishes available.

4. AMELIA Pendant Collection
3124 CM, Pages 211-212
Additional finishes available.





“Choose white slipcovers, linens, blues, sea grass and worn wood.”

CHRISTINA FLUEGGE, GREIGE DESIGN
SAN JOSE, CA



For more Style Guides, lighting ideas and tips from the pros, visit our Idea Centers on hinkleylighting.com

Fixtures shown: Congress Pendants 3133 AN, 3134 AN, 3135 AN, page 216;
Shown mounted to Accessory Canopy, FR83661BNI, page 318

MADE TO MEASURE

One of the most important considerations when selecting a chandelier for a specific space is its size and placement. Since chandeliers are designed to command attention or be a focal point, it's important to get it right. Here are some simple guidelines used by the pros:

Sizing Guidelines

DINING ROOM

To size a chandelier for your dining room, or to be the focal point of your space, measure the length and width of the room and add those figures together. The sum, converted to inches, will equal the diameter that you can use as a guideline when selecting the size of your chandelier.

**Example: 14' + 20' = 34' Converted to inches = 34"
Correct Size Chandelier = 34" Diameter**

If the resulting measurement (room length + width, converted to inches) seems inappropriate due to the size of your table, size your chandelier three quarters the width of your table.

In most cases, the bottom of your chandelier should sit approximately 30" - 32" above the table top.

FOYER

When determining whether to hang a flush, semi-flush, or multi-tiered chandelier in your foyer, be advised that the bottom of the fixture should be at least 7' from the floor.

For two-story foyers, if there is a window above the front door, center the chandelier so it can be seen from outside.

If your foyer is extra-large, you may also want to add sconces. Sconces should be installed 60" from the floor and 6'-8' apart.

"I TEND TO LIKE TO HANG OVER-SIZED CHANDELIERS IN SMALLER SPACES TO GIVE THE ROOM MORE DRAMA. I ALSO LOVE HANGING CHANDELIERS VERY LOW OVER A TABLE FOR THAT WOW FACTOR."

TAMARA KAYE-HONEY, HOUSE OF HONEY
LOS ANGELES



30"-32"

Standard suggested height above table.

"I like to mix old and new, shiny and dull, colorful and simple - all in one interior! I think by juxtaposing old and new, we create energy and interest in a space. A bit of cheeky with some very serious glam!"

TAMARA KAYE-HONEY, HOUSE OF HONEY
LOS ANGELES

SPLENDOR™

Splendor combines modern and traditional elements in a strong design that achieves an elegant, minimal effect. The 3/4" square arms and center column are balanced by a large solid metal ball finial and thick etched glass bobesche in Brushed Nickel.

FINISH Brushed Nickel

GLASS Etched Glass Bobesche



4928 BN



4922 BN



4924 BN



4926 BN

S P L E N D O R Brushed Nickel (BN)

ITEM	WIDTH/DIA.	HEIGHT	EXT.	DEPTH	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN	STEMS INCLUDED	BULBS	AVAILABLE FINISHES
4922 BN	14" W	14"	5"		11"	5" W, 6" H Back Plate			2-60w Cand.	BN
4924 BN	32½" W	15¼", 47½" Max.*		19"		6" W, 17¾" H Canopy	10' Wire	2-4", 2-6", 2-12" 2-18"	8-60w Cand.	BN
4926 BN	28½" Dia.	28¾", 66" Max.*				5" Dia. Canopy	10' Wire	1-4", 1-6", 2-12"	6-60w Cand.	BN
4928 BN	32½" Dia.	34", 71¼" Max.*				5" Dia. Canopy	10' Wire	1-4", 1-6", 2-12"	9-60w Cand.	BN
4512 BN	5/8" Dia.	12" (stem)								BN

*Maximum achievable height with stems included. Additional stems available, see above.

HARLOW™

Harlow's chic design is inspired by glamorous retro styling. The etched opal glass shade sits atop delicately bent, elongated arms in a Polished Nickel finish that transition to a cast oval step and onto a soft round center distributor.

FINISH Polished Nickel

GLASS Etched Opal



4218 PN



4210 PN



4213 PN



4216 PN

HARLOW Polished Nickel (PN)

ITEM	WIDTH/DIA.	HEIGHT	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN	STEMS INCLUDED	BULBS	AVAILABLE FINISHES
4210 PN	4½" W	14¼"	5"	10¼"	4½" W, 8" H Back Plate			1-60w Cand.	BC, PN
4213 PN	13¼" Dia.	15", 35½" Max.*			5¼" Dia. Canopy	10' Wire	1-6", 2-12"	3-60w Cand.	BC, PN
4216 PN	25" Dia.	15½", 53¾" Max.*			5¼" Dia. Canopy	10' Wire	1-6", 2-12", 1-18"	6-60w Cand.	BC, PN
4218 PN	29" Dia.	15½", 53¾" Max.*			5¼" Dia. Canopy	10' Wire	1-6", 2-12", 1-18"	8-60w Cand.	BC, PN
4312 PN	½" Dia.	12" (stem)							BC, PN

*Maximum achievable height with stems included. Additional stems available, see above.

HARLOW™

Harlow's chic design is inspired by glamorous retro styling. The etched opal glass shade sits atop delicately bent, elongated arms in a Brushed Caramel finish that transition to a cast oval step and onto a soft round center distributor.

FINISH Brushed Caramel

GLASS Etched Opal



4218 BC



4210 BC



4213 BC



4216 BC

HARLOW Brushed Caramel (BC)

ITEM	WIDTH/DIA.	HEIGHT	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN	STEMS INCLUDED	BULBS	AVAILABLE FINISHES
4210 BC	4½" W	14¼"	5"	10¼"	4½" W, 8" H Back Plate			1-60w Cand.	BC, PN
4213 BC	13¼" Dia.	15", 35½" Max.*			5¼" Dia. Canopy	10' Wire	1-6", 2-12"	3-60w Cand.	BC, PN
4216 BC	25" Dia.	15½", 53¾" Max.*			5¼" Dia. Canopy	10' Wire	1-6", 2-12", 1-18"	6-60w Cand.	BC, PN
4218 BC	29" Dia.	15½", 53¾" Max.*			5¼" Dia. Canopy	10' Wire	1-6", 2-12", 1-18"	8-60w Cand.	BC, PN
4312 BC	½" Dia.	12" (stem)							BC, PN

*Maximum achievable height with stems included. Additional stems available, see above.

ZELDA™

Zelda's striking mid-century silhouette features spheres that increase in size as they descend from the top loop, creating an elegant seamless center column. The sleek rectangular bowed arms support tapered etched glass shades perched on a hemisphere cup, adding vintage appeal.

FINISH Polished Nickel

GLASS Etched **SHADE** Textured Off-White Linen



3448 PN



3440 PN



3441 PN



3444 PN



3447 PN



3445 PN



3446 PN

ZELDA Polished Nickel (PN)

ITEM	WIDTH/DIA.	HEIGHT	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN	STEMS INCLUDED	BULBS	AVAILABLE FINISHES
3440 PN	5½" W	11¾"	5¾"	7"	5½" Dia. Back Plate			1-100w Med.	PN, VS
3441 PN	14¾" Dia.	12½"			5½" Dia. Canopy			3-100w Med.	PN, VS
3444 PN	20¼" Dia.	18½"			5½" Dia. Canopy	12', 10'		3-100w Med.	PN, VS
3445 PN	27" Dia.	18¾"			5½" Dia. Canopy	6', 5'		5-100w Med.	PN, VS
3446 PN	32" Dia.	23¼"			5½" Dia. Canopy	6', 5'		7-100w Med.	PN, VS
3447 PN	4¾" Dia.	12½", 44¾" Max.*			5½" Dia. Canopy	10' Wire	1-6", 2-12"	1-100w Med.	PN, VS
3448 PN	38" Dia.	26¼"			5½" Dia. Canopy	12', 10'		8-100w Med.	PN, VS
4312 PN	½" Dia.	12" (stem)							PN, VS

*Maximum achievable height with stems included. Additional stems available, see above.

ZELDA™

Zelda's striking mid-century silhouette features spheres that increase in size as they descend from the top loop, creating an elegant seamless center column. The sleek rectangular bowed arms support tapered etched glass shades perched on a hemisphere cup, adding vintage appeal.

FINISH Vintage Brass

GLASS Etched SHADE Textured Off-White Linen



3448 VS



3440 VS



3441 VS



3444 VS



3447 VS



3445 VS



3446 VS

ZELDA Vintage Brass (VS)

ITEM	WIDTH/DIA.	HEIGHT	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN	STEMS INCLUDED	BULBS	AVAILABLE FINISHES
3440 VS	5½" W	11¾"	5¾"	7"	5½" Dia. Back Plate			1-100w Med.	PN, VS
3441 VS	14¾" Dia.	12½"			5½" Dia. Canopy			3-100w Med.	PN, VS
3444 VS	20¼" Dia.	18½"			5½" Dia. Canopy	12', 10'		3-100w Med.	PN, VS
3445 VS	27" Dia.	18¾"			5½" Dia. Canopy	6', 5'		5-100w Med.	PN, VS
3446 VS	32" Dia.	23¼"			5½" Dia. Canopy	6', 5'		7-100w Med.	PN, VS
3447 VS	4¾" Dia.	12½", 44¾" Max.*			5½" Dia. Canopy	10' Wire	1-6", 2-12"	1-100w Med.	PN, VS
3448 VS	38" Dia.	26¼"			5½" Dia. Canopy	12', 10'		8-100w Med.	PN, VS
4312 VS	½" Dia.	12" (stem)							PN, VS

*Maximum achievable height with stems included. Additional stems available, see above.

MARGEAUX™

Margeaux's traditional style is reinforced by an impressive formal presence. This combination stem and chain hung collection features cast transition elements that extend from the circular body to the torchère arms, while the Polished Nickel finish complements this open airy design.

FINISH Polished Nickel

GLASS Etched Opal



3588 PN



3580 PN



3582 PN



3585 PN



3586 PN



3587 PN

MARGEAUX Polished Nickel (PN)

ITEM	WIDTH/DIA.	HEIGHT	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN	STEMS INCLUDED	BULBS	AVAILABLE FINISHES
3580 PN	4½" W	17¾"	5¾"	9½"	4½" W, 8" H Back Plate			1-100w Med.	PN, VS
3582 PN	12¾" W	17¾"	5¾"	9½"	4½" W, 8" H Back Plate			2-100w Med.	PN, VS
3585 PN	26" Dia.	21½", 64½" Max.*			5" Dia. Canopy	10' Wire	1-4", 1-6", 1-12", 1-18"	5-100w Med.	PN, VS
3586 PN	29" Dia.	24½", 67½" Max.*			5" Dia. Canopy	10' Wire	1-4", 1-6", 1-12", 1-18"	6-100w Med.	PN, VS
3587 PN	3½" W	14¼", 47¼" Max.*			5" Dia. Canopy	10' Wire	1-6", 2-12"	1-100w Med.	PN, VS
3588 PN	36" Dia.	32"			6" Dia. Canopy	12', 10'		8-100w Med.	PN, VS
6212 PN	5/8" Dia.	12" (stem)							PN, VS

*Maximum achievable height with stems included. Additional stems available, see above.

MARGEAUX™

Margeaux's traditional style is reinforced by an impressive formal presence. This combination stem and chain hung collection features cast transition elements that extend from the circular body to the torchère arms, while the Vintage Brass finish complements this open airy design.

FINISH Vintage Brass

GLASS Etched Opal



3588 VS



3580 VS



3582 VS



3585 VS



3586 VS



3587 VS

MARGE AUX Vintage Brass (VS)

ITEM	WIDTH/DIA.	HEIGHT	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN	STEMS INCLUDED	BULBS	AVAILABLE FINISHES
3580 VS	4½" W	17¾"	5¾"	9½"	4½" W, 8" H Back Plate			1-100w Med.	PN, VS
3582 VS	12¾" W	17¾"	5¾"	9½"	4½" W, 8" H Back Plate			2-100w Med.	PN, VS
3585 VS	26" Dia.	21½", 64½" Max.*			5" Dia. Canopy	10' Wire	1-4", 1-6", 1-12", 1-18"	5-100w Med.	PN, VS
3586 VS	29" Dia.	24½", 67½" Max.*			5" Dia. Canopy	10' Wire	1-4", 1-6", 1-12", 1-18"	6-100w Med.	PN, VS
3587 VS	3½" W	14¼", 47¼" Max.*			5" Dia. Canopy	10' Wire	1-6", 2-12"	1-100w Med.	PN, VS
3588 VS	36" Dia.	32"			6" Dia. Canopy	12', 10'		8-100w Med.	PN, VS
6212 VS	5⁄8" Dia.	12" (stem)							PN, VS

*Maximum achievable height with stems included. Additional stems available, see above.

PRINCETON™

Princeton's stem hung design features etched opal glass captured between matching metal trim rings that float above tapered cast stem details. The petite torch lights sit prominently on top of large rectangular arms for a bold yet elegant effect.

FINISH Brushed Nickel

GLASS Etched Opal Metal Trimmed Glass Shade



4078 BN



4071 BN

(shown mounted as semi-flush)



4071 BN



4070 BN



4076 BN



4073 BN

PRINCETON Brushed Nickel (BN)

ITEM	WIDTH/DIA.	HEIGHT	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN	STEMS INCLUDED	BULBS	AVAILABLE FINISHES
4070 BN	5½" W	16¾"	5¼"	12"	5½" Square Back Plate			1-60w Cand.	BN
4071 BN	17" Dia.	12½", 41½" Max.*			5½" Dia. Canopy	10' Wire	2-6", 2-12"	3-60w Cand.	BN
4073 BN	21" Dia.	19½", 49¾" Max.*			5¾" Dia. Canopy	10' Wire	1-4", 1-6", 1-12", 1-18"	3-60w Cand.	BN
4076 BN	28" Dia.	19½", 49¾" Max.*			5¾" Dia. Canopy	10' Wire	1-4", 1-6", 1-12", 1-18"	6-60w Cand.	BN
4078 BN	34" Dia.	29¼", 59½" Max.*			5¾" Dia. Canopy	10' Wire	1-4", 1-6", 1-12", 1-18"	9-60w Cand.	BN
4512 BN	5/8" Dia.	12" (stem)							BN

*Maximum achievable height with stems included. Additional stems available, see above.

MERIDIAN™


Meridian features minimal transitional styling with clean lines, soft curves and low-profile faceted ½" thick glass. This stem hung simplistic design will add a crisp focal point to any decor.

FINISH Brushed Nickel

GLASS Thick Faceted Clear Inside Etched



Meridian Bath,
pages 366-368



Scan to view a video of
the Meridian collection.

Top view of Meridian glass
showing ½" thickness



3878 BN



5590 BN



3870 BN



3874 BN



3871 BN



3877 BN



3875 BN



3872 BN



3873 BN

MERIDIAN Brushed Nickel (BN)

ITEM	WIDTH/DIA.	HEIGHT	EXT.	DEPTH	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN	STEMS INCLUDED	BULBS	AVAILABLE FINISHES
3870 BN	5" W	11¼"	6½"		4"	4½" W, 8" H Back Plate			1-60w G9**	BN, SK
3871 BN	16" Dia.	12¼"				5½" Dia. Canopy			3-60w G9**	BN, CM, SK
3872 BN	20" Dia.	23", 54½" Max.*				5½" Dia. Canopy	10' Wire	1-6", 2-12"	3-100w Med.	BN, SK
3873 BN	24" Dia.	18½", 51" Max.*				5½" Dia. Canopy	10' Wire	1-6", 2-12"	3-60w G9**	BN, SK
3874 BN	44" W	20", 51¼" Max.*		7½"		5½" Dia. Canopy	10' Wire	1-6", 2-12"	4-60w G9**	BN, SK
3875 BN	27" Dia.	18½", 50¾" Max.*				5½" Dia. Canopy	10' Wire	1-6", 2-12"	5-60w G9**	BN, SK
3877 BN	7½" Dia.	4¼", 36¾" Max.*				6" Dia. Canopy	10' Wire	1-6", 2-12"	1-60w G9**	BN, SK
3878 BN	34" Dia.	27", 98¼" Max.*				5½" Dia. Canopy	12', 5'		9-60w G9**	BN, SK
5590 BN	5" W	8"	6½"		4"	4½" W, 8" H Back Plate			1-60w G9**	BN, CM, SK
4312 BN	½" Dia.	12" (stem, 3877 BN only)								BN, SK
4512 BN	⅝" Dia.	12" (stem)								BN, SK

*Maximum achievable height with stems (or stems and chain) included. Additional stems available, see above. ** G9 halogen bulbs included.

MAKE A STATEMENT
 THREE TIER CHANDELIERS
 CREATE A DRAMATIC FOCAL POINT
 IN ANY LARGE SPACE



3876 SK



3876 BN



MERIDIAN Brushed Nickel (BN) and Satin Black (SK)

ITEM	WIDTH/DIA.	HEIGHT	DEPTH	BACK PLATE/CANOPY	WIRE/CHAIN	STEMS INCLUDED	BULBS	AVAILABLE FINISHES
3876 BN	34" Dia.	46¼", 119¼" Max.*		5½" Dia. Canopy	12', 5'	1-12"	12-60w G9**	BN, SK
3876 SK	34" Dia.	46¼", 119¼" Max.*		5½" Dia. Canopy	12', 5'	1-12"	12-60w G9**	BN, SK
4512 BN, SK	5/8" Dia.	12" (stem)						BN, SK

*Maximum achievable height with stems and chain included. Additional stems available, see above. **G9 halogen bulbs included.



MERIDIAN™


Meridian features minimal transitional styling with clean lines, soft curves and low-profile faceted ½" thick glass. This stem hung simplistic design will add a crisp focal point to any decor.

FINISH Satin Black

GLASS Thick Faceted Clear Inside Etched



Meridian Bath,
pages 366-368



Scan to view a video of
the Meridian collection.

Top view of Meridian glass
showing ½" thickness



3878 SK



5590 SK



3870 SK



3874 SK



3871 SK



3877 SK



3875 SK



3872 SK



3873 SK

MERIDIAN Satin Black (SK)

ITEM	WIDTH/DIA.	HEIGHT	EXT.	DEPTH	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN	STEMS INCLUDED	BULBS	AVAILABLE FINISHES
3870 SK	5" W	11¼"	6½"		4"	4½" W, 8" H Back Plate			1-60w G9**	BN, SK
3871 SK	16" Dia.	12¼"				5½" Dia. Canopy			3-60w G9**	BN, CM, SK
3872 SK	20" Dia.	23", 54½" Max.*				5½" Dia. Canopy	10' Wire	1-6", 2-12"	3-100w Med.	BN, SK
3873 SK	24" Dia.	18½", 51" Max.*				5½" Dia. Canopy	10' Wire	1-6", 2-12"	3-60w G9**	BN, SK
3874 SK	44" W	20", 51¼" Max.*		7½"		5½" Dia. Canopy	10' Wire	1-6", 2-12"	4-60w G9**	BN, SK
3875 SK	27" Dia.	18½", 50¾" Max.*				5½" Dia. Canopy	10' Wire	1-6", 2-12"	5-60w G9**	BN, SK
3877 SK	7½" Dia.	4¼", 36¾" Max.*				6" Dia. Canopy	10' Wire	1-6", 2-12"	1-60w G9**	BN, SK
3878 SK	34" Dia.	27", 98¼" Max.*				5½" Dia. Canopy	12', 5'		9-60w G9**	BN, SK
5590 SK	5" W	8"	6½"		4"	4½" W, 8" H Back Plate			1-60w G9**	BN, CM, SK
4312 SK	½" Dia.	12" (stem, 3877 SK only)								BN, SK
4512 SK	⅝" Dia.	12" (stem)								BN, SK

*Maximum achievable height with stems (or stems and chain) included. Additional stems available, see above. ** G9 halogen bulbs included.

MIDTOWN™

Midtown's clean, transitional design features an over scaled center column in Brushed Nickel with a faceted ribbed pattern on the etched glass cylinders.

FINISH Brushed Nickel

GLASS Multi-Faceted Etched



4978 BN



4970 BN



4972 BN



4971 BN



4975 BN



4976 BN

MIDTOWN Brushed Nickel (BN)

ITEM	WIDTH/DIA.	HEIGHT	EXT.	DEPTH	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN	STEMS INCLUDED	BULBS	AVAILABLE FINISHES
4970 BN	5" W	8"	6¼"		4"	5" W, 8" H Back Plate			1-100w Med.	BN
4971 BN	18" Dia.	11¼"				6" Dia. Canopy			3-100w Med.	BN
4972 BN	18" Dia.	19½"				6" Dia. Canopy	12', 10'		3-100w Med.	BN
4975 BN	24" Dia.	22¼"				6" Dia. Canopy	6', 5'		5-100w Med.	BN
4976 BN	28" Dia.	24"				6" Dia. Canopy	6', 5'		6-100w Med.	BN
4978 BN	32" Dia.	29"				6" Dia. Canopy	12', 10'		9-100w Med.	BN

PIPER™

Piper's clean, minimal styling has a retro edge. The tall, cylindrical glass combined with a clean finish reinforce its sleek, transitional design, accentuated by cast detailing and vertical light reflectors.

FINISH Brushed Nickel

GLASS Etched Opal



4868 BN



4860 BN



4865 BN

PIPER Brushed Nickel (BN)

ITEM	WIDTH/DIA.	HEIGHT	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN	STEMS INCLUDED	BULBS	AVAILABLE FINISHES
4860 BN	4½" W	12¾"	6"	7¼"	4½" W, 11" H Back Plate			1-100w Med.	BN
4865 BN	26" W	22½"			5¼" Dia. Canopy	6', 5'		5-100w Med.	BN
4868 BN	32" W	29"			5¼" Dia. Canopy	12', 10'		9-100w Med.	BN

MONACO™

Monaco features “C” shaped arms finished with a hanging crystal ball ornament. This contemporary, stem-hung design is ideal for low ceiling mounting situations.

FINISH Brushed Nickel

GLASS Etched Opal Metal Trimmed Glass Shade



4856 BN



4850 BN



4852 BN



4851 BN



4853 BN



4855 BN



4858 BN

MONACO Brushed Nickel (BN)

ITEM	WIDTH/DIA.	HEIGHT	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN	STEMS INCLUDED	BULBS	AVAILABLE FINISHES
4850 BN	6¼" W	10¼"	10¾"	5¼"	5" W, 5¼" H Back Plate			1-60w Cand.**	BC, BN
4851 BN	5" W	20"	9¾"	10"	5" W, 5¼" H Back Plate			1-100w Med.	BC, BN
4852 BN	20" W	10¼"	10¾"	5¼"	5" W, 5¼" H Back Plate			2-60w Cand.**	BC, BN
4853 BN	25½" Dia.	11½", 49" Max.*			6" Dia. Canopy	10' Wire	1-4', 1-6", 2-12"	3-60w Cand.**	BC, BN
4855 BN	27¾" Dia.	12½", 50" Max.*			6" Dia. Canopy	10' Wire	1-4', 1-6", 2-12"	5-60w Cand.**	BC, BN
4856 BN	31½" Dia.	14½", 52" Max.*			6" Dia. Canopy	10' Wire	1-4', 1-6", 2-12"	6-60w Cand.**	BC, BN
4858 BN	26¾" Dia.	40", 65¾" Max.*			6" Dia. Canopy	10' Wire	2-6", 2-12"	4-100w Med.	BC, BN
4512 BN	⅝" Dia.	12" (stem)							BN

*Maximum achievable height with stems included. Additional stems available, see above. **Recommend G16½ or 60w E-12 lamp, sold separately (0060W-E12).

MONACO™

Monaco features “C” shaped arms finished with a hanging crystal ball ornament. This contemporary, stem-hung design is ideal for low ceiling mounting situations.

FINISH Brushed Caramel

GLASS Etched Opal Metal Trimmed Glass Shade



4856 BC



4850 BC



4852 BC



4851 BC



4853 BC



4855 BC



4858 BC

MONACO Brushed Caramel (BC)

ITEM	WIDTH/DIA.	HEIGHT	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN	STEMS INCLUDED	BULBS	AVAILABLE FINISHES
4850 BC	6¼" W	10¼"	10¾"	5¼"	5" W, 5¼" H Back Plate			1-60w Cand.**	BC, BN
4851 BC	5" W	20"	9¾"	10"	5" W, 5¼" H Back Plate			1-100w Med.	BC, BN
4852 BC	20" W	10¼"	10¾"	5¼"	5" W, 5¼" H Back Plate			2-60w Cand.**	BC, BN
4853 BC	25¼" Dia.	11½", 49" Max.*			6" Dia. Canopy	10' Wire	1-4', 1-6", 2-12"	3-60w Cand.**	BC, BN
4855 BC	27¾" Dia.	12½", 50" Max.*			6" Dia. Canopy	10' Wire	1-4', 1-6", 2-12"	5-60w Cand.**	BC, BN
4856 BC	31½" Dia.	14½", 52" Max.*			6" Dia. Canopy	10' Wire	1-4', 1-6", 2-12"	6-60w Cand.**	BC, BN
4858 BC	26¾" Dia.	40", 65¾" Max.*			6" Dia. Canopy	10' Wire	2-6", 2-12"	4-100w Med.	BC, BN
6212 BC	⅝" Dia.	12" (stem)							BC

*Maximum achievable height with stems included. Additional stems available, see above. **Recommend G16½ or 60w E-12 lamp, sold separately (0060W-E12).

CHANNING™

Channing's strong transitional design is softened by graceful curves in Brushed Nickel. The refined, tapered laser cut arms allow for a delicate glimpse of the etched opal glass for an added layer of style.

FINISH Brushed Nickel

GLASS Etched Opal



4228 BN



4220 BN



4225 BN



4224 BN

CHANNING Brushed Nickel (BN)

ITEM	WIDTH/DIA.	HEIGHT	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN	STEMS INCLUDED	BULBS	AVAILABLE FINISHES
4220 BN	4½" W	18½"	7¼"	13"	4½" W, 8¼" H Back Plate			1-100w Med.	BN
4224 BN	21¼" Dia.	24", 60½" Max.*			5" Dia. Canopy	10' Wire	2-6", 2-12"	3-100w Med.	BN
4225 BN	27" Dia.	29", 75¼" Max.*			5" Dia. Canopy	10' Wire	1-4", 1-6", 1-12, 1-24"	5-100w Med.	BN
4228 BN	32" Dia.	33½", 79½" Max.*			6½" Dia. Canopy	10' Wire	1-4", 1-6", 1-12, 1-24"	9-100w Med.	BN
4312 BN	½" Dia.	12" (stem)							BN

*Maximum achievable height with stems included. Additional stems available, see above.

DARIEN™

Darien cleverly combines overscaled proportions and heavy ¾" square tubing with wide low-profile etched opal glass to create a new modern classic. The elegant and graceful design of the fixture's curves is accentuated by the Polished Antique Nickel finish.

FINISH Polished Antique Nickel

GLASS Etched Opal



3966 PL



3960 PL



3961 PL



3963 PL



3965 PL

DARIEN Polished Antique Nickel (PL)

ITEM	WIDTH/DIA.	HEIGHT	EXT.	DEPTH	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN	STEMS INCLUDED	BULBS	AVAILABLE FINISHES
3960 PL	6¾" W	15½"	8¾"		6"	5¾" Dia. Back Plate			1-60w G9*	PL
3961 PL	16" Dia.	11½"				6¾" Dia. Canopy			3-100w Med.	PL
3963 PL	26¾" Dia.	22¼"				5¾" Dia. Canopy	6', 5'		3-60w G9*	PL
3965 PL	30" Dia.	26½"				5¾" Dia. Canopy	6', 5'		5-60w G9*	PL
3966 PL	37½" Dia.	32¾"				5¾" Dia. Canopy	12', 10'		6-60w G9*	PL

*G9 halogen bulbs included.

DILLON™

Dillon's contemporary, stem hung design features a floating cast double ring intersection as the centerpiece. The absence of a center tube contributes an airy grace to its robust ¾" tube construction.

FINISH Brushed Nickel

GLASS Etched Opal



3668 BN



3662 BN



3661 BN



3664 BN



3667 BN



3660 BN



3665 BN



3663 BN

DILLON Brushed Nickel (BN)

ITEM	WIDTH/DIA.	HEIGHT	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN	STEMS INCLUDED	BULBS	AVAILABLE FINISHES
3660 BN	6" W	7 ³ / ₄ "	7 ¹ / ₂ "	4"	4 ³ / ₄ " W, 7" H Back Plate			1-100w Med.	BN
3661 BN	15" Dia.	7 ³ / ₄ "			15" Dia. Canopy			2-60w Med.	BN
3662 BN	18 ¹ / ₄ " Dia.	11"			5" Dia. Canopy			3-100w Med.	BN
3663 BN	23" Dia.	19 ¹ / ₄ ", 68" Max.*			5" Dia. Canopy	10' Wire	1-4", 1-6", 1-12", 1-24"	3-100w Med.	BN
3664 BN	20" Dia.	22", 70 ³ / ₄ " Max.*			5" Dia. Canopy	10' Wire	1-4", 1-6", 1-12", 1-24"	3-100w Med.	BN
3665 BN	26" Dia.	22", 70 ³ / ₄ " Max.*			5" Dia. Canopy	10' Wire	1-4", 1-6", 1-12", 1-24"	5-100w Med.	BN
3667 BN	6" Dia.	7 ¹ / ₄ ", 40" Max.*			5" Dia. Canopy	10' Wire	1-6", 2-12"	1-100w Med.	BN
3668 BN	29 ¹ / ₄ " Dia.	26 ³ / ₄ ", 70 ¹ / ₂ " Max.*			5" Dia. Canopy	10' Wire	1-4", 1-6", 1-12", 1-24"	9-100w Med.	BN
4312 BN	1/2" Dia.	12" (stem, 3667 BN only)							BN
6066 BN	5/8" Dia.	12" (stem)							BN

*Maximum achievable height with stems included. Additional stems available, see above.

VICTORY™

Victory features three unique triangular plates that create a modern pyramid design, concealing the center wire way. The contemporary angled arms in a Brushed Nickel finish reinforce the triangular theme, adding minimalist flair to this chic style.

FINISH Brushed Nickel

GLASS Etched Opal



4138 BN



4134 BN



4130 BN



4136 BN



4133 BN

VICTORY Brushed Nickel (BN)

ITEM	WIDTH/DIA.	HEIGHT	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN	STEMS INCLUDED	BULBS	AVAILABLE FINISHES
4130 BN	6" W	15¼"	6"	13"	6" W, 15¼" H Back Plate			1-100w Med.	BN
4133 BN	20½" Dia.	21¾", 70¼" Max.*			5" Dia. Canopy	10' Wire	1-4", 1-6", 1-12", 1-24"	3-100w Med.	BN
4134 BN	20" Dia.	23½", 71¼" Max.*			5" Dia. Canopy	10' Wire	1-4", 1-6", 1-12", 1-24"	3-100w Med.	BN
4136 BN	27" Dia.	28", 76½" Max.*			5" Dia. Canopy	10' Wire	1-4", 1-6", 1-12", 1-24"	6-100w Med.	BN
4138 BN	31" Dia.	31¾", 79¼" Max.*			5" Dia. Canopy	10' Wire	1-4", 1-6", 1-12", 1-24"	9-100w Med.	BN
6066 BN	⅝" Dia.	12" (stem)							BN

*Maximum achievable height with stems included. Additional stems available, see above.

VALLEY™

Valley offers a contemporary twist on a traditional style, with glass shades that transition from square on the bottom to round at the top to complement the fixture's smooth curved overlapping arm design.

FINISH Brushed Nickel

GLASS Etched Opal



4708 BN



4701 BN



4702 BN



4700 BN



4707 BN



4705 BN



4704 BN



4703 BN

VALLEY Brushed Nickel (BN)

ITEM	WIDTH/DIA.	HEIGHT	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN	STEMS INCLUDED	BULBS	AVAILABLE FINISHES
4700 BN	5¼" W	21"	7¼"	10½"	4½" W, 4¾" H Back Plate			1-100w Med.	BN, VK
4701 BN	18½" Dia.	12¼"			5¼" Dia. Canopy			2-100w Med.	BN, VK
4702 BN	23" Dia.	13¾"			5½" Dia. Canopy			3-100w Med.	BN, VK
4703 BN	19" Dia.	27"			5¾" Dia. Canopy	6', 5'		3-100w Med.	BN, VK
4704 BN	23¾" Dia.	26½"			5¾" Dia. Canopy	12', 10'		3-100w Med.	BN, VK
4705 BN	27" Dia.	33¼"			5¾" Dia. Canopy	6', 5'		5-100w Med.	BN, VK
4707 BN	5¼" Dia.	12¼", 45¼" Max.*			5¾" Dia. Canopy	10' Wire	1-6", 2-12"	1-100w Med.	BN, VK
4708 BN	32" Dia.	37¼"			5¾" Dia. Canopy	12', 10'		9-75w Med.	BN, VK
4312 BN	½" Dia.	12" (stem)							BN, VK

*Maximum achievable height with stems included. Additional stems available, see above.

VALLEY™

Valley offers a contemporary twist on a traditional style, with glass shades that transition from square on the bottom to round at the top to complement the fixture's smooth curved overlapping arm design.

FINISH Vintage Black

GLASS Iridescent Amber



4708 VK



4701 VK



4702 VK



4700 VK



4707 VK



4705 VK



4704 VK



4703 VK

VALLEY Vintage Black (VK)

ITEM	WIDTH/DIA.	HEIGHT	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN	STEMS INCLUDED	BULBS	AVAILABLE FINISHES
4700 VK	5¼" W	21"	7¼"	10½"	4½" W, 4¾" H Back Plate			1-100w Med.	BN, VK
4701 VK	18½" Dia.	12¼"			5¼" Dia. Canopy			2-100w Med.	BN, VK
4702 VK	23" Dia.	13¾"			5½" Dia. Canopy			3-100w Med.	BN, VK
4703 VK	19" Dia.	27"			5¾" Dia. Canopy	6', 5'		3-100w Med.	BN, VK
4704 VK	23¾" Dia.	26½"			5¾" Dia. Canopy	12', 10'		3-100w Med.	BN, VK
4705 VK	27" Dia.	33¼"			5¾" Dia. Canopy	6', 5'		5-100w Med.	BN, VK
4707 VK	5¼" Dia.	12¼", 45¼" Max.*			5¾" Dia. Canopy	10' Wire	1-6", 2-12"	1-100w Med.	BN, VK
4708 VK	32" Dia.	37¼"			5¾" Dia. Canopy	12', 10'		9-75w Med.	BN, VK
4312 VK	½" Dia.	12" (stem)							BN, VK

*Maximum achievable height with stems included. Additional stems available, see above.

HAMPTON™

Hampton is a modern transitional design, offering the ultimate in urban sophistication. The minimal, rectangular frame, paired with a decorative acrylic etched bottom lens, is softened by a contemporary off-white linen drum shade.

FINISH Antique Nickel

SHADE Off-White Linen Hardback



3206 AN





3201 AN



3200 AN



3211 AN



3203 AN



3205 AN



3204 AN



HAMPTON Antique Nickel (AN)

ITEM	WIDTH/DIA.	HEIGHT	EXT.	DEPTH	TOPTO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN	STEMS INCLUDED	BULBS	AVAILABLE FINISHES
3200 AN	15" Dia.	11¾"				9¾" Dia. Canopy			3-60w Med.	AN, BR
3201 AN	20" Dia.	12"				11¾" Dia. Canopy			3-75w Med.	AN, BR
3203 AN	20" Dia.	26½"				5" Dia. Canopy	12', 5'		3-60w Med.	AN, BR
3204 AN	26" Dia.	30¼"				5" Dia. Canopy	12', 5'		3-100w Med.	AN, BR
3205 AN	16" Dia.	32¾"				5" Dia. Canopy	12', 10'		3-60w Med.	AN, BR
3206 AN	30" Dia.	33"				5" Dia. Canopy	12', 10'		3-100w Med.	AN, BR
3211 AN	26" Dia.	14½"				15¾" Dia. Canopy			3-100w Med.	AN, BR



HAMPTON Antique Nickel (AN)

ITEM	WIDTH/DIA.	HEIGHT	EXT.	DEPTH	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN	STEMS INCLUDED	BULBS	AVAILABLE FINISHES
3202 AN	15" W	12"	5½"		4"	4½" W, 12" H Back Plate			2-60w Cand.	AN, BR
3207 AN	7" Dia.	11¾", 44" Max.*				5" Dia. Canopy	10' Wire	1-6", 2-12"	1-100w Med.	AN, BR
3208 AN	40" W	31"		18"		4½" W, 7" L Canopy	12', 5'		4-100w Med.	AN, BR
3209 AN	24¾" Dia.	24½"				5" Dia. Canopy	12', 10'		4-100w Med.	AN, BR
3210 AN	6¾" W	12"	8¾"		6"	4¾" W, 12" H Back Plate			1-100w Med.	AN, BR
3214 AN	29" W	24"				5" Dia. Canopy	12', 10'		4-100w Med.	AN, BR
4312 AN	½" Dia.	12" (stem)								AN, BR

*Maximum achievable height with stems included. Additional stems available, see above.

Hampton is a modern transitional design, offering the ultimate in urban sophistication. The minimal, rectangular frame, paired with a decorative acrylic etched bottom lens, is softened by a contemporary off-white linen drum shade.

HAMPTON™

Brushed Bronze FINISH
Off-White Linen Hardback SHADE



3206 BR 



3201 BR



3200 BR



3211 BR



3203 BR



3205 BR



3204 BR



HAMPTON Brushed Bronze (BR)

ITEM	WIDTH/DIA.	HEIGHT	EXT.	DEPTH	TOPTO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN	STEMS INCLUDED	BULBS	AVAILABLE FINISHES
3200 BR	15" Dia.	11¾"				9¾" Dia. Canopy			3-60w Med.	AN, BR
3201 BR	20" Dia.	12"				11¾" Dia. Canopy			3-75w Med.	AN, BR
3203 BR	20" Dia.	26½"				5" Dia. Canopy	12', 5'		3-60w Med.	AN, BR
3204 BR	26" Dia.	30¼"				5" Dia. Canopy	12', 5'		3-100w Med.	AN, BR
3205 BR	16" Dia.	32¾"				5" Dia. Canopy	12', 10'		3-60w Med.	AN, BR
3206 BR	30" Dia.	33"				5" Dia. Canopy	12', 10'		3-100w Med.	AN, BR
3211 BR	26" Dia.	14½"				15¾" Dia. Canopy			3-100w Med.	AN, BR



3208 BR



3210 BR



3202 BR



3207 BR



3214 BR



3209 BR

HAMPTON Brushed Bronze (BR)

ITEM	WIDTH/DIA.	HEIGHT	EXT.	DEPTH	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN	STEMS INCLUDED	BULBS	AVAILABLE FINISHES
3202 BR	15" W	12"	5½"		4"	4½" W, 12" H Back Plate			2-60w Cand.	AN, BR
3207 BR	7" Dia.	11¾, 44" Max.*				5" Dia. Canopy	10' Wire	1-6", 2-12"	1-100w Med.	AN, BR
3208 BR	40" W	31"		18"		4½" W, 7" L Canopy	12', 5'		4-100w Med.	AN, BR
3209 BR	24¾" Dia.	24½"				5" Dia. Canopy	12', 10'		4-100w Med.	AN, BR
3210 BR	6¾" W	12"	8¾"		6"	4¾" W, 12" H Back Plate			1-100w Med.	AN, BR
3214 BR	29" W	24"				5" Dia. Canopy	12', 10'		4-100w Med.	AN, BR
4312 BR	½" Dia.	12" (stem)								AN, BR

*Maximum achievable height with stems included. Additional stems available, see above.

FLOURISH™

Flourish features a sophisticated design of overlapping metal circles in a Silver Leaf finish. The elegant rectangular cage, paired with a decorative etched bottom lens, complements the metallic linen shade for a boutique designer feel.

FINISH Silver Leaf
SHADE Metallic Linen



3287 SL



FLOURISH Silver Leaf (SL)

ITEM	WIDTH/DIA.	HEIGHT	EXT.	DEPTH	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN	STEMS INCLUDED	BULBS	AVAILABLE FINISHES
3281 SL	15" Square	13½"				5½" Square Canopy			3-60w Med.	SL
3282 SL	9" W	16½"	4"	8"		6" W, 8" H Back Plate			2-60w Cand.	SL
3284 SL	16" Square	27½", 60" Max.*				5½" Square Canopy	10' Wire	1-6", 2-12"	4-60w Cand.	SL
3285 SL	18" Square	10½", 43" Max.*				5½" Square Canopy	10' Wire	1-6", 2-12"	3-100w Med.	SL
3286 SL	20" Square	33½", 66" Max.*				5½" Square Canopy	10' Wire	1-6", 2-12"	6-60w Cand.	SL
3287 SL	32" W	11½", 44" Max.*		10"		10" W, 5" L Canopy	10' Wire	2-6", 4-12"	4-100w Med.	SL
6063 SL	⅝" Dia.	12" (stem)								SL

*Maximum achievable height with stems included. Additional stems available, see above.

CIRRUS™

Cirrus' contemporary hardback shade in an ivory linen flows in a modern continuous soft curve. The Brushed Nickel finish and decorative etched acrylic bottom lens complete its chic, minimalist style.

FINISH Brushed Nickel

SHADE Ivory Fabric Hardback



3806 BN
(mounted as semi-flush)



3806 BN



3800 BN



(3800 BN sconce, top view)



3802 BN



3802 BN
(mounted as semi-flush)



3804 BN



3804 BN
(mounted as semi-flush)



3805 BN



3805 BN
(mounted as semi-flush)



3804 BN and 3805 BN can be installed with or without 8" decorative plate.



CIRRUS Brushed Nickel (BN)

ITEM	WIDTH/DIA.	HEIGHT	EXT.	DEPTH	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN	STEMS INCLUDED	BULBS	AVAILABLE FINISHES
3800 BN	15" W	6½"	4"		3¼"	13¼" W, 5½" H Back Plate			2-60w Cand.	BN
3802 BN	36" W	11½", 54" Max.**		23"		4¾" W, 16½" L Canopy	10' Wire	2-4", 2-6", 2-12", 2-24"	6-100w Med.	BN
3804 BN	20" W	12", 56" Max.**				5" Dia. Canopy	10' Wire	1-4", 1-6", 1-12", 1-24"	4-60w Med.	BN
3805 BN	28" W	12", 56" Max.**				5" Dia. Canopy	10' Wire	1-4", 1-6", 1-12", 1-24"	4-75w Med.	BN
3806 BN	48" W	11½", 54" Max.**		8½"		4¾" W, 16½" L Canopy	10' Wire	2-4", 2-6", 2-12", 2-24"	6-75w Med.	BN
6066 BN	5/8" Dia.	12" (stem)								BN

*Minimum height when mounting semi-flush to the ceiling (4" stems must be used). **Maximum achievable height with stems included. Additional stems available, see above.

LANZA™

Lanza makes a chic statement with its strong, rectangular metal work. This contemporary style features geometric detailing, a casual untrimmed oatmeal linen shade and an acrylic lens for sophisticated, modern appeal.

FINISH Oil Rubbed Bronze

SHADE Oatmeal Linen



Lanza Bath,
pages 372-373



3163 OZ



3161 OZ



3162 OZ



(3162 OZ sconce, top view)



3164 OZ

LANZA Oil Rubbed Bronze (OZ)

ITEM	WIDTH/DIA.	HEIGHT	EXT.	DEPTH	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN	STEMS INCLUDED	BULBS	AVAILABLE FINISHES
3161 OZ	15¼" Square	10½"				5" Square Canopy			3-100w Med.	OZ
3162 OZ	10"	11½"	4"		3.5	5½" W, 5¾" H Back Plate			2-60w Cand.	OZ
3163 OZ	18" Square	21¼", 58" Max.*				5" Square Canopy	10' Wire	1-4", 1-6", 2-12"	3-100w Med.	OZ
3164 OZ	15¼" Square	20", 56½" Max.*				5" Square Canopy	10' Wire	1-4", 1-6", 2-12"	3-100w Med.	OZ
6066 OZ	⅝" Dia.	12" (stem)								OZ

*Maximum achievable height with stems included. Additional stems available, see above.

HATHAWAY™

Hathaway's striking design features a bold shade held in place by three intersecting, floating arms with unique forged uprights and ring detail for a modern style. Available in Antique Nickel with etched glass or Olde Bronze with etched amber glass.

FINISH Antique Nickel, Olde Bronze

GLASS Etched (Antique Nickel), Etched Amber (Olde Bronze)



3224 AN



3224 OB





3221 AN



3221 OB



3220 AN



3220 OB



3222 AN



3222 OB



HATHAWAY Antique Nickel (AN), Olde Bronze (OB)

ITEM	WIDTH/DIA.	HEIGHT	EXT.	DEPTH	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN	STEMS INCLUDED	BULBS	AVAILABLE FINISHES
3220 AN	16" Dia.	11¾"				5¾" Dia. Canopy			3-100w Med.	AN, OB
3220 OB	16" Dia.	11¾"				5¾" Dia. Canopy			3-100w Med.	AN, OB
3221 AN	20¾" Dia.	12¼"				5¾" Dia. Canopy			4-100w Med.	AN, OB
3221 OB	20¾" Dia.	12¼"				5¾" Dia. Canopy			4-100w Med.	AN, OB
3222 AN	20¾" Dia.	26½", 59½" Max.*				5" Dia. Canopy	10' Wire	1-6", 2-12"	4-100w Med.	AN, OB
3222 OB	20¾" Dia.	26½", 59½" Max.*				5" Dia. Canopy	10' Wire	1-6", 2-12"	4-100w Med.	AN, OB
3224 AN	26¾" Dia.	29¼", 62¼" Max.*				5" Dia. Canopy	10' Wire	1-6", 2-12"	5-100w Med.	AN, OB
3224 OB	26¾" Dia.	29¼", 62¼" Max.*				5" Dia. Canopy	10' Wire	1-6", 2-12"	5-100w Med.	AN, OB
6066 AN	5/8" Dia.	12" (stem)								AN, OB
6066 OB	5/8" Dia.	12" (stem)								AN, OB

*Maximum achievable height with stems included. Additional stems available, see above.

CORDILLERA™

Cordillera conveys contemporary chic with tall tubular glass, three-quarter trim rings and dramatic scaling. The Rustic Iron finish is paired with light scavo glass to complete this bold design.

FINISH Rustic Iron
GLASS Light Scavo



Cordillera Outdoor,
pages 556-557



4099 RI



4090 RI



4095 RI



4094 RI



4097 RI

CORDILLERA Rustic Iron (RI)

ITEM	WIDTH/DIA.	HEIGHT	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN	STEMS INCLUDED	BULBS	AVAILABLE FINISHES
4090 RI	7½ W	22"	6½"	13¼"	5½" W, 10" H Back Plate			1-60w Cand.	RI
4094 RI	19" Dia.	36"			7¼" Dia. Canopy	6', 5'		8-40w Cand.	RI
4095 RI	25" Dia.	25¼"			7¼" Dia. Canopy	6', 5'		10-40w Cand., 1-100w Med.	RI
4097 RI	7½" Dia.	22½", 55½" Max.*			7¼" Dia. Canopy	10' Wire	1-6", 2-12"	1-100w Med.	RI
4099 RI	25½" Dia.	46"			7¼" Dia. Canopy	12', 10'		10-60w Cand.	RI
4312 RI	½" Dia.	12" (stem)							RI

*Maximum achievable height with stems included. Additional stems available, see above.


MONDRIAN™


Mondrian's unique patterned panels of glass mounted in copper foil adds geometric panache in a Buckeye Bronze finish.


FINISH Buckeye Bronze

GLASS Copper Foil Bound Glass Panels

4576 KZ

4571 KZ
(mounted as semi-flush)


4572 KZ
(sconce)


4570 KZ
(sconce)


4571 KZ


4575 KZ

4574 KZ

4577 KZ

MONDRIAN Buckeye Bronze (KZ)

ITEM	WIDTH/DIA.	HEIGHT	EXT.	DEPTH	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN	STEMS INCLUDED	BULBS	AVAILABLE FINISHES
4570 KZ	7" W	11"	4"		5½"	7" W, 10½" H Back Plate			2-60w Cand.	KZ
4571 KZ	16" W	12", 13¼"		16"		7" W Canopy	6', 5'		4-60w Cand.	KZ
4572 KZ	7" W	24"	4"		12"	7" W, 23" H Back Plate			3-60w Cand.	KZ
4574 KZ	14" W	26"		14"		7" W Canopy	6', 5'		4-60w Cand.	KZ
4575 KZ	36" W	24"		12"		4½" W, 12¼" L Canopy	6', 5'		5-60w Cand.	KZ
4576 KZ	14" W	42"		14"		7" W Canopy	12', 10'		12-60w Cand.	KZ
4577 KZ	7" W	11½", 43½" Max.**		7"		5" W Canopy	10' Wire	1-6", 2-12"	1-100w Med.	KZ
4312 KZ	½" Dia.	12" (stem)								KZ

*Height when hung with chain. **Maximum achievable height with stems included. Additional stems available, see above.

BOLLA™

The graceful lines of Bolla's sweeping double arms create a soft elegance while heavy cast spheres perched at the tips add to its innovative style. The strong proportions of the arms contrast with the subtle bell shaped glass, combining both traditional and modern details.

FINISH Brushed Nickel


GLASS Etched Opal



Bolla Bath,
pages 388-390



Bolla Outdoor,
pages 486-489



Scan to view a video
of the Bolla collection.



4659 BN





4655 BN



4653 BN



4667 BN



4656 BN



4657 BN

BOLLA Brushed Nickel (BN)

ITEM	WIDTH/DIA.	HEIGHT	EXT.	DEPTH	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN	STEMS INCLUDED	BULBS	AVAILABLE FINISHES
4653 BN	22½" Dia.	18"				6" Dia. Canopy	6', 5'		3-100w Med.	BN, BR, OB
4655 BN	24" Dia.	24"				6" Dia. Canopy	6', 5'		5-100w Med.	BN, BR, OB
4656 BN	29" Dia.	29"				6" Dia. Canopy	6', 5'		6-100w Med.	BN, BR, OB
4657 BN	35" Dia.	37½"				6" Dia. Canopy	12', 10'		9-100w Med.	BN, BR, OB
4659 BN	48" Dia.	48½"				6" Dia. Canopy	12', 10'		18-60w Med.	BN, BR, OB
4667 BN	7¾" Dia.	7¼", 39½" Max.*				5¼" Dia. Canopy	10' Wire	1-6", 2-12"	1-100w Med.	BN, BR, OB
4312 BN	½" Dia.	12" (stem)								BN, BR, OB

*Maximum achievable height with stems included. Additional stems available, see above.



BOLLA Brushed Nickel (BN)

ITEM	WIDTH/DIA.	HEIGHT	EXT.	DEPTH	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN	STEMS INCLUDED	BULBS	AVAILABLE FINISHES
4650 BN	7¾" W	8½"	8¾"		3½"	6" W, 7½" Back Plate			1-100w Med.	BN, BR, OB
4661 BN	15½" Dia.	8¼, 48" Max.*				6" Dia. Canopy	10', 5'	3-12"	1-100w Med.	BN, BR, OB
4662 BN	44¼" W	26½"		15½"		6" Dia. Canopy	6', 5'		2-100w Med.	BN, BR, OB
4663 BN	16" Dia.	28¾"				6" Dia. Canopy	6', 5'		3-60w Cand.	BN, BR, OB
4666 BN	56" W	25¼"		15½"		6" Dia. Canopy	6', 5'		3-100w Med.	BN, BR, OB
4670 BN	7¾" W	20½"	10¼"		15"	6" W, 7½" H Back Plate			1-100w Med.	BN, BR, OB
4312 BN	½" Dia.	12" (stem)								BN, BR, OB

*Maximum achievable height with stems and chain included. Additional stems available, see above.



4660 BN



4651 BN



4669 BN



4652 BN



4665 BN



4664 BN



BOLLA Brushed Nickel (BN)

ITEM	WIDTH/DIA.	HEIGHT	EXT.	DEPTH	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN	STEMS INCLUDED	BULBS	AVAILABLE FINISHES
4651 BN	19¼" Dia.	14"				6" Dia. Canopy			2-100w Med.	BN, BR, OB
4652 BN	23¼" Dia.	26½"				6" Dia. Canopy	6', 5'		3-100w Med.	BN, BR, OB
4660 BN	16¾" Dia.	8"				5" Dia. Canopy			2-75w Med.	BN, BR, OB
4664 BN	30" Dia.	32"				6" Dia. Canopy	12', 10'		4-75w Med.	BN, BR, OB
4665 BN	18" Dia.	44"				6" Dia. Canopy	12', 10'		6-60w Cand.	BN, BR, OB
4669 BN	23¼" Dia.	16"				6" Dia. Canopy			3-100w Med.	BN, BR, OB

BOLLA™

The graceful lines of Bolla's sweeping double arms create a soft elegance while heavy cast spheres perched at the tips add to its innovative style. The strong proportions of the arms contrast with the subtle bell shaped glass, combining both traditional and modern details.

FINISH Olde Bronze


GLASS Light Amber Seedy



BollaBath,
pages 388-390



Bolla Outdoor,
pages 486-489



Scan to view a video
of the Bolla collection.



4659 OB





4655 OB



4653 OB



4667 OB



4656 OB



4657 OB

BOLLA Olde Bronze (OB)

ITEM	WIDTH/DIA.	HEIGHT	EXT.	DEPTH	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN	STEMS INCLUDED	BULBS	AVAILABLE FINISHES
4653 OB	22½" Dia.	18"				6" Dia. Canopy	6', 5'		3-100w Med.	BN, BR, OB
4655 OB	24" Dia.	24"				6" Dia. Canopy	6', 5'		5-100w Med.	BN, BR, OB
4656 OB	29" Dia.	29"				6" Dia. Canopy	6', 5'		6-100w Med.	BN, BR, OB
4657 OB	35" Dia.	37½"				6" Dia. Canopy	12', 10'		9-100w Med.	BN, BR, OB
4659 OB	48" Dia.	48½"				6" Dia. Canopy	12', 10'		18-60w Med.	BN, BR, OB
4667 OB	7¾" Dia.	7¼", 39½" Max.*				5¼" Dia. Canopy	10' Wire	1-6", 2-12"	1-100w Med.	BN, BR, OB
4312 OB	½" Dia.	12" (stem)								BN, BR, OB

*Maximum achievable height with stems included. Additional stems available, see above.



BOLLA Olde Bronze (OB)

ITEM	WIDTH/DIA.	HEIGHT	EXT.	DEPTH	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN	STEMS INCLUDED	BULBS	AVAILABLE FINISHES
4650 OB	7¾" W	8½"	8¾"		3½"	6" W, 7½" Back Plate			1-100w Med.	BN, BR, OB
4661 OB	15½" Dia.	8¼", 48" Max.*				6" Dia. Canopy	10', 5'	3-12"	1-100w Med.	BN, BR, OB
4662 OB	44¼" W	26½"		15½"		6" Dia. Canopy	6', 5'		2-100w Med.	BN, BR, OB
4663 OB	16" Dia.	28¾"				6" Dia. Canopy	6', 5'		3-60w Cand.	BN, BR, OB
4666 OB	56" W	25¼"		15½"		6" Dia. Canopy	6', 5'		3-100w Med.	BN, BR, OB
4670 OB	7¾" W	20½"	10¼"		15"	6" W, 7½" H Back Plate			1-100w Med.	BN, BR, OB
4312 OB	½" Dia.	12" (stem)								BN, BR, OB

*Maximum achievable height with stems and chain included. Additional stems available, see above.



4660 OB



4651 OB



4669 OB



4652 OB



4665 OB



4664 OB



BOLLA Olde Bronze (OB)

ITEM	WIDTH/DIA.	HEIGHT	EXT.	DEPTH	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN	STEMS INCLUDED	BULBS	AVAILABLE FINISHES
4651 OB	19¼" Dia.	14"				6" Dia. Canopy			2-100w Med.	BN, BR, OB
4652 OB	23¼" Dia.	26½"				6" Dia. Canopy	6', 5'		3-100w Med.	BN, BR, OB
4660 OB	16¾" Dia.	8"				5" Dia. Canopy			2-75w Med.	BN, BR, OB
4664 OB	30" Dia.	32"				6" Dia. Canopy	12', 10'		4-75w Med.	BN, BR, OB
4665 OB	18" Dia.	44"				6" Dia. Canopy	12', 10'		6-60w Cand.	BN, BR, OB
4669 OB	23¼" Dia.	16"				6" Dia. Canopy			3-100w Med.	BN, BR, OB

BOLLA™

The graceful lines of Bolla's sweeping double arms create a soft elegance while heavy cast spheres perched at the tips add to its innovative style. The strong proportions of the arms contrast with the subtle bell shaped glass, combining both traditional and modern details.

FINISH Brushed Bronze


GLASS Light Amber Seedy



Bolla Bath,
pages 388-390



Bolla Outdoor,
pages 486-489



Scan to view a video
of the Bolla collection



4659 BR





4653 BR



4655 BR



4667 BR



4656 BR



4657 BR

BOLLA Brushed Bronze (BR)

ITEM	WIDTH/DIA.	HEIGHT	EXT.	DEPTH	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN	STEMS INCLUDED	BULBS	AVAILABLE FINISHES
4653 BR	22½" Dia.	18"				6" Dia. Canopy	6', 5'		3-100w Med.	BN, BR, OB
4655 BR	24" Dia.	24"				6" Dia. Canopy	6', 5'		5-100w Med.	BN, BR, OB
4656 BR	29" Dia.	29"				6" Dia. Canopy	6', 5'		6-100w Med.	BN, BR, OB
4657 BR	35" Dia.	37½"				6" Dia. Canopy	12', 10'		9-100w Med.	BN, BR, OB
4659 BR	48" Dia.	48½"				6" Dia. Canopy	12', 10'		18-60w Med.	BN, BR, OB
4667 BR	7¾" Dia.	7¼", 39½" Max.*				5¼" Dia. Canopy	10' Wire	1-6", 2-12"	1-100w Med.	BN, BR, OB
4312 BR	½" Dia.	12" (stem)								BN, BR, OB

*Maximum achievable height with stems included. Additional stems available, see above.



BOLLA Brushed Bronze (BR)

ITEM	WIDTH/DIA.	HEIGHT	EXT.	DEPTH	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN	STEMS INCLUDED	BULBS	AVAILABLE FINISHES
4650 BR	7¾" W	8½"	8¾"		3½"	6" W, 7½" Back Plate			1-100w Med.	BN, BR, OB
4661 BR	15½" Dia.	8¼", 48" Max.*				6" Dia. Canopy	10', 5'	3-12"	1-100w Med.	BN, BR, OB
4662 BR	44¼" W	26½"		15½"		6" Dia. Canopy	6', 5'		2-100w Med.	BN, BR, OB
4663 BR	16" Dia.	28¾"				6" Dia. Canopy	6', 5'		3-60w Cand.	BN, BR, OB
4666 BR	56" W	25¼"		15½"		6" Dia. Canopy	6', 5'		3-100w Med.	BN, BR, OB
4670 BR	7¾" W	20½"	10¼"		15"	6" W, 7½" H Back Plate			1-100w Med.	BN, BR, OB
4312 BR	½" Dia.	12" (stem)								BN, BR, OB

*Maximum achievable height with stems and chain included. Additional stems available, see above.



4660 BR



4651 BR



4669 BR



4652 BR



4665 BR



4664 BR



BOLLA Brushed Bronze (BR)

ITEM	WIDTH/DIA.	HEIGHT	EXT.	DEPTH	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN	STEMS INCLUDED	BULBS	AVAILABLE FINISHES
4651 BR	19¼" Dia.	14"				6" Dia. Canopy			2-100w Med.	BN, BR, OB
4652 BR	23¼" Dia.	26½"				6" Dia. Canopy	6', 5'		3-100w Med.	BN, BR, OB
4660 BR	16¾" Dia.	8"				5" Dia. Canopy			2-75w Med.	BN, BR, OB
4664 BR	30" Dia.	32"				6" Dia. Canopy	12', 10'		4-75w Med.	BN, BR, OB
4665 BR	18" Dia.	44"				6" Dia. Canopy	12', 10'		6-60w Cand.	BN, BR, OB
4669 BR	23¼" Dia.	16"				6" Dia. Canopy			3-100w Med.	BN, BR, OB

WHITNEY™

Whitney features classic “S” curved arms that extend from the clean, tapered center column in a Brushed Nickel finish. The sleek design is complemented by the bold cast metal ball details, transitioning into a metal candle sleeve and textured, off-white linen shade.

FINISH Brushed Nickel

SHADE Off-White Linen



4618 BN



4610 BN



4613 BN



4611 BN
(mounted as semi-flush)



4611 BN



4615 BN



4616 BN

WHITNEY Brushed Nickel (BN)

ITEM	WIDTH/DIA.	HEIGHT	EXT.	DEPTH	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN	STEMS INCLUDED	BULBS	AVAILABLE FINISHES
4610 BN	9" W	15"	11"		11½"	6" Dia. Back Plate			1-60w Cand.	BN
4611 BN	15" Dia.	21", 16½"				6" Dia. Canopy	6', 5'		3-60w Cand.	BN
4613 BN	21½" Dia.	25¼"				6" Dia. Canopy	6', 5'		3-60w Cand.	BN
4615 BN	28" Dia.	22¾"				6" Dia. Canopy	6', 5'		5-60w Cand.	BN
4616 BN	32" Dia.	25½"				6" Dia. Canopy	6', 5'		6-60w Cand.	BN
4618 BN	36¼" Dia.	26"				6" Dia. Canopy	12', 10'		9-60w Cand.	BN

*Body height when hung with chain (includes loop).

BRANTLEY™


Brantley's transitional design features bold arms that sweep outward, creating a striking effect, while geometric castings and decorative twin arm construction add to its beauty. The Brushed Nickel finish is complemented by etched white glass.

FINISH Brushed Nickel

GLASS Etched White



Brantley Bath,
page 383



Scan to view a video of
the Brantley collection



4639 BN





4631 BN



4632 BN



4630 BN



4633 BN



4637 BN



4638 BN



4636 BN

BRANTLEY Brushed Nickel (BN)

ITEM	WIDTH/DIA.	HEIGHT	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN	STEMS INCLUDED	BULBS	AVAILABLE FINISHES
4630 BN	4¾" W	12¼"	8½"	7"	4¾" W, 10" H Back Plate			1-100w Med.	BN, OZ, TB
4631 BN	17" Dia.	7"						3-60w Med.	BN, OZ, TB
4632 BN	17" Dia.	10¾"			5" Dia. Canopy			3-100w Med.	BN, OZ, TB
4633 BN	22½" Dia.	22"			5" Dia. Canopy	6', 5'		3-100w Med.	BN, OZ, TB
4636 BN	29¾" Dia.	26¼"			5" Dia. Canopy	6', 5'		6-100w Med.	BN, OZ, TB
4637 BN	4¾" Dia.	17", 41¼" Max.*			5" Dia. Canopy	10' Wire	1-6", 2-12"	1-100w Med.	BN, OZ, TB
4638 BN	33¼" Dia.	32¾"			5" Dia. Canopy	12', 10'		9-75w Med.	BN, OZ, TB
4639 BN	43" Dia.	34"			5" Dia. Canopy	12', 10'		12-60w Med.	BN, OZ, TB
4312 BN	½" Dia.	12" (stem)							BN, OZ, TB

*Maximum achievable height with stems included. Additional stems available, see above.

BRANTLEY™


Brantley's transitional design features bold arms that sweep outward, creating a striking effect, while geometric castings and decorative twin arm construction add to its beauty. The Oil Rubbed Bronze finish is paired with marbled amber glass.

FINISH Oil Rubbed Bronze

GLASS Marbled Amber



Brantley Bath,
page 383



Scan to view a video of
the Brantley collection



4639 OZ





4631 OZ



4632 OZ



4630 OZ



4633 OZ



4637 OZ



4638 OZ



4636 OZ

BRANTLEY Oil Rubbed Bronze (OZ)

ITEM	WIDTH/DIA.	HEIGHT	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN	STEMS INCLUDED	BULBS	AVAILABLE FINISHES
4630 OZ	4¾" W	12¼"	8½"	7"	4¾" W, 10" H Back Plate			1-100w Med.	BN, OZ, TB
4631 OZ	17" Dia.	7"						3-60w Med.	BN, OZ, TB
4632 OZ	17" Dia.	10¾"			5" Dia. Canopy			3-100w Med.	BN, OZ, TB
4633 OZ	22½" Dia.	22"			5" Dia. Canopy	6', 5'		3-100w Med.	BN, OZ, TB
4636 OZ	29¾" Dia.	26¼"			5" Dia. Canopy	6', 5'		6-100w Med.	BN, OZ, TB
4637 OZ	4¾" Dia.	17", 41¼" Max.*			5" Dia. Canopy	10' Wire	1-6", 2-12"	1-100w Med.	BN, OZ, TB
4638 OZ	33¼" Dia.	32¾"			5" Dia. Canopy	12', 10'		9-75w Med.	BN, OZ, TB
4639 OZ	43" Dia.	34"			5" Dia. Canopy	12', 10'		12-60w Med.	BN, OZ, TB
4312 OZ	½" Dia.	12" (stem)							BN, OZ, TB

*Maximum achievable height with stems included. Additional stems available, see above.

BRANTLEY™


Brantley's transitional design features bold arms that sweep outward, creating a striking effect, while geometric castings and decorative twin arm construction add to its beauty. The Textured Black finish is complemented by etched white glass.

FINISH Textured Black

GLASS Etched White



Brantley Bath,
page 383



Scan to view a video of
the Brantley collection



4639 TB





4631 TB



4632 TB



4630 TB



4633 TB



4637 TB



4638 TB



4636 TB

BRANTLEY Textured Black (TB)

ITEM	WIDTH/DIA.	HEIGHT	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN	STEMS INCLUDED	BULBS	AVAILABLE FINISHES
4630 TB	4¾" W	12¼"	8½"	7"	4¾" W, 10" H Back Plate			1-100w Med.	BN, OZ, TB
4631 TB	17" Dia.	7"						3-60w Med.	BN, OZ, TB
4632 TB	17" Dia.	10¾"			5" Dia. Canopy			3-100w Med.	BN, OZ, TB
4633 TB	22½" Dia.	22"			5" Dia. Canopy	6', 5'		3-100w Med.	BN, OZ, TB
4636 TB	29¾" Dia.	26¼"			5" Dia. Canopy	6', 5'		6-100w Med.	BN, OZ, TB
4637 TB	4¾" Dia.	17", 41¼" Max.*			5" Dia. Canopy	10' Wire	1-6", 2-12"	1-100w Med.	BN, OZ, TB
4638 TB	33¼" Dia.	32¾"			5" Dia. Canopy	12', 10'		9-75w Med.	BN, OZ, TB
4639 TB	43" Dia.	34"			5" Dia. Canopy	12', 10'		12-60w Med.	BN, OZ, TB
4312 TB	½" Dia.	12" (stem)							BN, OZ, TB

*Maximum achievable height with stems included. Additional stems available, see above.

PARKER™

Parker's decorative double arm construction, combined with a Buckeye Bronze finish and light etched amber linen glass, creates a smooth, curved design with crisp, transitional details.

FINISH Buckeye Bronze

GLASS Light Amber Etched Linen



4439 KZ



4430 KZ



4431 KZ



4434 KZ



4433 KZ



4438 KZ



4436 KZ



4437 KZ

PARKER Buckeye Bronze (KZ)

ITEM	WIDTH/DIA.	HEIGHT	EXT.	TOPTO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN	STEMS INCLUDED	BULBS	AVAILABLE FINISHES
4430 KZ	5¼" W	12"	6¼"	4"	5¼" W, 12" H Back Plate			1-100w Med.	KZ
4431 KZ	16" Dia.	12¾"			6" Dia. Canopy			2-100w Med.	KZ
4433 KZ	22" Dia.	23"			6" Dia. Canopy	6', 5'		3-100w Med.	KZ
4434 KZ	20" Dia.	24½"			6" Dia. Canopy	12', 10'		3-100w Med.	KZ
4436 KZ	26¼" Dia.	23½"			6" Dia. Canopy	6', 5'		6-100w Med.	KZ
4437 KZ	4¾" Dia.	14¼", 46½" Max.*			6" Dia. Canopy	10' Wire	1-6", 2-12"	1-100w Med.	KZ
4438 KZ	32¼" Dia.	32¾"			6" Dia. Canopy	12', 10'		9-75w Med.	KZ
4439 KZ	42¼" Dia.	34"			6" Dia. Canopy	12', 10'		12-60w Med.	KZ
4312 KZ	½" Dia.	12" (stem)							KZ

*Maximum achievable height with stems included. Additional stems available, see above.

THISTLEDOWN™

Thistledown is an updated traditional design with smooth, flowing transitions that blend into an industrial yoke-mount center stem. The Victorian Bronze finish complements its amber linen glass for a warm elegance.

FINISH Victorian Bronze
GLASS Amber Linen



Thistledown Outdoor,
pages 558-559



4179 VZ





4174 VZ



4173 VZ



4177 VZ



4176 VZ



4178 VZ

THISTLEDOWN Victorian Bronze (VZ)

ITEM	WIDTH/DIA.	HEIGHT	DEPTH	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN	STEMS INCLUDED	BULBS	AVAILABLE FINISHES
4173 VZ	15¼" Dia.	23"			5¾" Dia. Canopy	6', 5'		3-100w Med.	VZ
4174 VZ	47" W	24½"	13¾"		5¾" Dia. Canopy	6', 5'		3-100w Med.	VZ
4176 VZ	26½" Dia.	25½"			5¾" Dia. Canopy	6', 5'		6-100w Med.	VZ
4177 VZ	5¼" Dia.	10½", 43½" Max.*			5¾" Dia. Canopy	10' Wire	1-6", 2-12"	1-100w Med.	VZ
4178 VZ	30½" Dia.	39½"			5¾" Dia. Canopy	12', 10'		9-75w Med.	VZ
4179 VZ	41½" Dia.	50½"			5¾" Dia. Canopy	12', 10'		15-60w Med.	VZ
4312 VZ	½" Dia.	12" (stem)							VZ

*Maximum achievable height with stems included. Additional stems available, see above.



4170 VZ



4171 VZ



4505 VZ



5680 VZ



4508 VZ



THISTLEDOWN Victorian Bronze (VZ)

ITEM	WIDTH/DIA.	HEIGHT	EXT.	DEPTH	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN	STEMS INCLUDED	BULBS	AVAILABLE FINISHES
4170 VZ	15" Dia.	13"				5¾" Dia. Canopy			3-75w Med.	VZ
4171 VZ	15¼" Dia.	8"							3-60w Med.	VZ
4505 VZ	25" Dia.	34½", 38"**				5" Dia. Canopy	6', 5'		5-100w Med.	VZ
4508 VZ	36" Dia.	45¼", 48½"**				5" Dia. Canopy	12', 10'		8-100w Med.	VZ
5680 VZ	5¾" W	12¼"	7¾"		9½"	5¾" Dia. Back Plate			1-100w Med.	VZ

**Height when hung with chain (includes loop).



STOWE™

Stowe features hand-forged iron work in a unique Metro Copper finish with subtle red copper hues that complement the antique light scavo glass. The bold curves and sharp lines of this transitional style create an elegant yet modern look.

FINISH Metro Copper

GLASS Antique Light Scavo



Stowe Bath,
page 392



4729 MC

50



4721 MC



4724 MC



4720 MC



4727 MC



4725 MC



4728 MC

STOWE Metro Copper (MC)

ITEM	WIDTH/DIA.	HEIGHT	EXT.	DEPTH	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN	STEMS INCLUDED	BULBS	AVAILABLE FINISHES
4720 MC	5" W	14"	6½"		6¾"	4" W, 7" H Back Plate			1-100w Med.	MC
4721 MC	15½" Dia.	6¾"							2-75w Med.	MC
4724 MC	22" Dia.	24"				7" Dia. Canopy	12', 10'		3-75w Med.	MC
4725 MC	23" Dia.	22½"				7" Dia. Canopy	6', 5'		5-100w Med.	MC
4727 MC	5" Dia.	10½", 43¾" Max.*				7" Dia. Canopy	10' Wire	1-6", 2-12"	1-100w Med.	MC
4728 MC	30" Dia.	27½"				7" Dia. Canopy	12', 10'		9-75w Med.	MC
4729 MC	42" Dia.	36"				7" Dia. Canopy	12', 10'		15-60w Cand.	MC
4312 MC	½" Dia.	12" (stem)								MC

*Maximum achievable height with stems included. Additional stems available, see above.

LAUREN™

The transitional style of the Lauren collection features sweeping, intersecting rectangular arms in a Victorian Bronze finish. The etched opal trumpet glass sits inside a “floating” metal ring, adding to its rustic-chic appeal.

FINISH Victorian Bronze

GLASS Etched Opal

Top view showing Lauren's
forged ring and captured glass



4068 VZ



4063 VZ



4064 VZ



4067 VZ



4062 VZ



4061 VZ



4060 VZ



4065 VZ

LAUREN Victorian Bronze (VZ)

ITEM	WIDTH/DIA.	HEIGHT	EXT.	DEPTH	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN	STEMS INCLUDED	BULBS	AVAILABLE FINISHES
4060 VZ	6" W	14¼"	7"		8¾"	4¾" W, 8¾" H Back Plate			1-60w Cand.	VZ
4061 VZ	20¼" Dia.	10½"				4¾" Dia. Canopy			2-100w Med.	VZ
4062 VZ	32½" Dia.	25¾"				4¾" Dia. Canopy	12', 10'		3-100w Med.	VZ
4063 VZ	23¾" Dia.	22"				4¾" Dia. Canopy	6', 5'		3-60w Cand.	VZ
4064 VZ	41¾" Dia.	24¾"		7"		4¾" W, 11" L Canopy	6', 5'		4-60w Cand.	VZ
4065 VZ	29½" Dia.	24"				4¾" Dia. Canopy	6', 5'		5-60w Cand.	VZ
4067 VZ	7¾" W	15", 47¼" Max.*				4¾" Dia. Canopy	10' Wire	1-6", 2-12"	1-60w Cand.	VZ
4068 VZ	38¼" Dia.	29¾"				4¾" Dia. Canopy	12', 10'		7-60w Cand.	VZ
6035 VZ	½" Dia.	12" (stem)								VZ

*Maximum achievable height with stems included. Additional stems available, see above.

MARION™

Marion's sweeping arms are styled in a minimalist, forged iron design and flow dramatically downward to the finished candle sleeves. The open middle features a large glass sphere hanging from its decorative stem.

FINISH Textured Black

SHADE Oatmeal Linen (selected items only)



4478 TB

When ordering sconce with shade,
please indicate SKU for both.



4470 TB (sconce)
8471 SH (shade)



4470 TB



4475 TB



4474 TB



4473 TB

MARION Textured Black (TB)

ITEM	WIDTH/DIA.	HEIGHT	EXT.	TOPTO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN	STEMS INCLUDED	BULBS	AVAILABLE FINISHES
4470 TB	4½" W	17"	7"	12"	4½" W, 9½" H Back Plate			1-60w Cand.	TB
4473 TB	29½" Dia.	29"			5" Dia. Canopy	6', 5'		5-60w Cand.	TB
4474 TB	22" Dia.	28"			5" Dia. Canopy	12', 10'		4-60w Cand.	TB
4475 TB	25" Dia.	22½"			5" Dia. Canopy	6', 5'		5-60w Cand.	TB
4478 TB	30" Dia.	30½"			5" Dia. Canopy	12', 10'		9-60w Cand.	TB
8471 SH	9½" W	6½"	5½"						

CASA™

Casa makes the most of its fine details: individually unique antique scavo glass, twisted wrought iron and hand-forged scrollwork in an Olde Black finish complete its rustic-chic appeal with a Southwestern flair.

FINISH Olde Black
GLASS Antique Scavo



Casa Bath,
page 394



Casa Outdoor,
pages 554-555



4309 OL





4013 OL



3508 OL



3503 OL



4018 OL



4019 OL



4015 OL

50

CASA Olde Black (OL)

ITEM	WIDTH/DIA.	HEIGHT	EXT.	DEPTH	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN	STEMS INCLUDED	BULBS	AVAILABLE FINISHES
3503 OL	12½" Dia.	17½"				5" Dia. Canopy	12', 10'		3-60w Cand.	OL
3508 OL	36" W	24¼"		23"		5" W, 7" L Canpy	6' 5"		6-100w Med.	OL
4013 OL	16¾" Dia.	18½"				5" Dia. Canopy	6' 5"		3-100w Med.	OL
4015 OL	25" Dia.	25½"				5" Dia. Canopy	6' 5"		5-100w Med.	OL
4018 OL	28½" Dia.	32"				5" Dia. Canopy	12', 10'		9-100w Med.	OL
4019 OL	42" Dia.	45½"				6" Dia. Canopy	12', 10'		15-60w Med.	OL
4309 OL	56" Dia.	68"				6½" Dia. Canopy	12', 10'		18-60w Med.	OL



4016 OL



4300 OL



4308 OL



4010 OL



3502 OL



3506 OL



3504 OL

CASA Olde Black (OL)

ITEM	WIDTH/DIA.	HEIGHT	EXT.	DEPTH	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN	STEMS INCLUDED	BULBS	AVAILABLE FINISHES
3502 OL	14¼" Dia.	21"				5" Dia. Canopy	6', 5'		3-60w Cand.	OL
3504 OL	17¾" Dia.	29¼"				5" Dia. Canopy	6', 5'		3-100w Med.	OL
3506 OL	22½" Dia.	41"				5" Dia. Canopy	12', 10'		6-100w Med.	OL
4010 OL	5" W	10¾"	6"		6¾"	5" W, 7¾" H Back Plate			1-100w Med.	OL
4016 OL	38" W	24½"		24"		5" W, 7" L Canopy	6', 5'		8-75w Med.	OL
4300 OL	5" W	24"	4"		11"	5" W, 7¾" H Back Plate			1-100w Med.	OL
4308 OL	36½" W	30"				6½" Dia. Canopy	12', 10'		8-100w Med.	OL



3501 OL



4311 OL



4011 OL



4304 OL



4017 OL



4314 OL



4316 OL



4313 OL



CASA Olde Black (OL)

ITEM	WIDTH/DIA.	HEIGHT	EXT.	DEPTH	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN	STEMS INCLUDED	BULBS	AVAILABLE FINISHES
3501 OL	14¼" Dia.	8¾"							3-60w Med.	OL
4011 OL	13" Dia.	12"				5" Dia. Canopy			2-60w Med.	OL
4017 OL	5½" Dia.	13", 45" Max.*				5" Dia. Canopy	10' Wire	1-6", 2-12"	1-100w Med.	OL
4304 OL	54" W	28½"		5"		5" W, 7" L Canopy	6', 5'		6-100w Med.	OL
4311 OL	23" Dia.	14"				5¾" Dia. Canopy			3-100w Med.	OL
4313 OL	22¼" Dia.	26½"				6¼" Dia. Canopy	6', 5'		3-75w Med.	OL
4314 OL	27¼" Dia.	32"				6¼" Dia. Canopy	6', 5'		4-75w Med.	OL
4316 OL	38½" Dia.	41¼"				6¼" Dia. Canopy	6', 5'		6-75w Med.	OL
4312 OL	½" Dia.	12" (stem)								OL

*Maximum achievable height with stems included. Additional stems available, see above.

SLOAN™

Sloan's modern interpretation of the traditional forged chandelier makes a strong statement in a dark Regency Bronze finish with bold arms and oatmeal linen hardback shades.

FINISH Regency Bronze

SHADE Oatmeal Linen



4548 RB



4541 RB



4540 RB



4543 RB



4544 RB



4547 RB



4542 RB



4545 RB



4546 RB

SLOAN Regency Bronze (RB)

ITEM	WIDTH/DIA.	HEIGHT	EXT.	DEPTH	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN	STEMS INCLUDED	BULBS	AVAILABLE FINISHES
4540 RB	4¾" W	16"	6¾"		8¼"	4¾" W, 12" H Back Plate			1-60w Cand.	RB
4541 RB	16" Dia.	10½"				5½" Dia. Canopy			2-75w Med.	RB
4542 RB	24" Dia.	23"				6" Dia. Canopy	12', 10'		3-100w Med.	RB
4543 RB	24" Dia.	14"				5½" Dia. Canopy			3-100w Med.	RB
4544 RB	50" W	25"		4¾"		4¾" W, 12" L Canopy	6', 5'		5-60w Cand.	RB
4545 RB	26" Dia.	25½"				6" Dia. Canopy	6', 5'		5-60w Cand.	RB
4546 RB	28" Dia.	28½"				6" Dia. Canopy	6', 5'		6-60w Cand.	RB
4547 RB	6" Dia.	15", 50" Max.*				6" Dia. Canopy	10' Wire	1-6", 2-12"	1-100w Med.	RB
4548 RB	36" Dia.	35½"				6" Dia. Canopy	12', 10'		9-60w Cand.	RB
4512 RB	5/8" Dia.	12" (stem)								RB

*Maximum achievable height with stems included. Additional stems available, see above.

SUSSEX™

Sussex offers traditional charm with an edge of modern luxury. The Brushed Nickel finish, white fabric hardback shade and clear glass column and candles adds to its sophistication.

FINISH Brushed Nickel

GLASS White Fabric Hardback



4799 BN



4792 BN



4900 BN



4790 BN



4796 BN



4798 BN

SUSSEX Brushed Nickel (BN)

ITEM	WIDTH/DIA.	HEIGHT	EXT.	DEPTH	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN	STEMS INCLUDED	BULBS	AVAILABLE FINISHES
4790 BN	4½" W	17¾"	6¾"		10¾"	4½" W, 14" H Back Plate			1-60w Cand.	BN, EZ
4792 BN	15½" W	15¾"	6¾"		8¾"	4½" W, 14" H Back Plate			2-60w Cand.	BN, EZ
4796 BN	36¾" W	25"		22¾"		4½" W, 14" L Canopy	6', 5'		6-60w Cand.	BN, EZ
4798 BN	32" Dia.	34½"				6¾" Dia. Canopy	12', 10'		9-60w Cand.	BN, EZ
4799 BN	47" Dia.	44¼"				6¾" Dia. Canopy	12', 10'		15-40w Cand.	BN, EZ
4900 BN	14" W	14"	4"		7"	4½" W, 14" H Back Plate			2-60w Cand.	BN, EZ



4793 BN



4797 BN



4791 BN



4795 BN



4794 BN

SUSSEX Brushed Nickel (BN)

ITEM	WIDTH/DIA.	HEIGHT	EXT.	DEPTH	TOPTO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN	STEMS INCLUDED	BULBS	AVAILABLE FINISHES
4791 BN	16" Dia.	15"				6¾" Dia. Canopy			3-75w Med.	BN, EZ
4793 BN	16" Dia.	19¼"				6¾" Dia. Canopy	6', 5'		3-60w Cand.	BN, EZ
4794 BN	22" Dia.	26¾"				6¾" Dia. Canopy	12', 10'		3-75w Med.	BN, EZ
4795 BN	26" Dia.	24¾"				6¾" Dia. Canopy	6', 5'		5-60w Cand.	BN, EZ
4797 BN	23" Dia.	24"				6½" Dia. Canopy	12', 10'		4-60w Cand.	BN, EZ

Sussex offers traditional charm with an edge of modern luxury. The English Bronze finish, ivory fabric hardback shade and clear glass column and candles adds to its sophistication.

SUSSEX™

English Bronze FINISH
Ivory Fabric Hardback GLASS



4799 EZ



4792 EZ



4900 EZ



4790 EZ



4796 EZ



4798 EZ

SUSSEX English Bronze (EZ)

ITEM	WIDTH/DIA.	HEIGHT	EXT.	DEPTH	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN	STEMS INCLUDED	BULBS	AVAILABLE FINISHES
4790 EZ	4½" W	17¾"	6¾"		10¾"	4½" W, 14" H Back Plate			1-60w Cand.	BN, EZ
4792 EZ	15½" W	15¾"	6¾"		8¾"	4½" W, 14" H Back Plate			2-60w Cand.	BN, EZ
4796 EZ	36¾" W	25"		22¾"		4½" W, 14" L Canopy	6', 5'		6-60w Cand.	BN, EZ
4798 EZ	32" Dia.	34½"				6¾" Dia. Canopy	12', 10'		9-60w Cand.	BN, EZ
4799 EZ	47" Dia.	44¼"				6¾" Dia. Canopy	12', 10'		15-40w Cand.	BN, EZ
4900 EZ	14" W	14"	4"		7"	4½" W, 14" H Back Plate			2-60w Cand.	BN, EZ



4793 EZ



4797 EZ



4791 EZ



4795 EZ



4794 EZ

SUSSEX English Bronze (EZ)

ITEM	WIDTH/DIA.	HEIGHT	EXT.	DEPTH	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN	STEMS INCLUDED	BULBS	AVAILABLE FINISHES
4791 EZ	16" Dia.	15"				6¾" Dia. Canopy			3-75w Med.	BN, EZ
4793 EZ	16" Dia.	19¼"				6¾" Dia. Canopy	6', 5'		3-60w Cand.	BN, EZ
4794 EZ	22" Dia.	26¾"				6¾" Dia. Canopy	12', 10'		3-75w Med.	BN, EZ
4795 EZ	26" Dia.	24¾"				6¾" Dia. Canopy	6', 5'		5-60w Cand.	BN, EZ
4797 EZ	23" Dia.	24"				6½" Dia. Canopy	12', 10'		4-60w Cand.	BN, EZ

DUNHILL™

Dunhill's traditional style features painted antique candle sleeves and sturdy round detailing in a Royal Bronze finish. The off-white pleated fabric shades and vintage-inspired faux alabaster glass add classic details for an authentic look.

FINISH Royal Bronze

SHADE Off-White Pleated Fabric GLASS Vintage Faux Alabaster



4599 RY



4590 RY



4594 RY



4591 RY



4595 RY



4598 RY

DUNHILL Royal Bronze (RY)

ITEM	WIDTH/DIA.	HEIGHT	EXT.	DEPTH	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN	STEMS INCLUDED	BULBS	AVAILABLE FINISHES
4590 RY	6¼" W	11¼"	8½"		5½"	6" Dia. Back Plate			1-60w Cand.	RY
4591 RY	16" Dia.	13"				6" Dia. Canopy			2-100w Med.	RY
4594 RY	20" Dia.	27½"				6" Dia. Canopy			3-100w Med.	RY
4595 RY	27¼" Dia.	26"				6" Dia. Canopy	6', 5'		5-60w Cand.	RY
4598 RY	37" Dia.	38¼"				6" Dia. Canopy	12', 10'		9-60w Cand.	RY
4599 RY	45" Dia.	42½"				6" Dia. Canopy	12', 10'		12-60w Cand.	RY

TRUMAN™

The traditional style of the Truman collection features boldly sloped arms that uniquely contrast with its elegant cast finials. The Antique Nickel finish highlights the beautiful etched opal glass shades.

FINISH Antique Nickel

GLASS Etched Opal



4028 AN



4021 AN



4023 AN



4020 AN



4027 AN



4024 AN



4025 AN

TRUMAN *Antique Nickel (AN)*

ITEM	WIDTH/DIA.	HEIGHT	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN	STEMS INCLUDED	BULBS	AVAILABLE FINISHES
4020 AN	5¼" W	12¾"	7¾"	9"	4½" W, 9" H Back Plate			1-100w Med.	AN
4021 AN	16" Dia.	12"			6½" Dia. Canopy			3-100w Med.	AN
4023 AN	20" Dia.	22¼"			5¾" Dia. Canopy	6', 5'		3-100w Med.	AN
4024 AN	21¼" Dia.	24"			5¾" Dia. Canopy	6', 5'		4-100w Med.	AN
4025 AN	27" Dia.	26½"			5¾" Dia. Canopy	6', 5'		5-100w Med.	AN
4027 AN	5¼" Dia.	9", 41¾" Max.*			5¾" Dia. Canopy	10' Wire	1-6", 2-12"	1-100w Med.	AN
4028 AN	30" Dia.	32¼"			5¾" Dia. Canopy	12', 10'		9-100w Med.	AN
4312 AN	½" Dia.	12" (stem)							AN

*Maximum achievable height with stems included. Additional stems available, see above.

MAYFLOWER™

Mayflower offers a bold, traditional design in a lustrous Olde Bronze finish with inside etched amber glass. The unique yoke-mount glass holders and decorative cast tension knob detailing add authentic flair.

FINISH Olde Bronze

GLASS Inside Etched Amber



4168 OB



5670 OB



4167 OB



4161 OB



4151 OB



4166 OB



4162 OB

MAYFLOWER Olde Bronze (OB)

ITEM	WIDTH/DIA.	HEIGHT	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN	STEMS INCLUDED	BULBS	AVAILABLE FINISHES
4151 OB	14" Dia.	9", 42½" Max.*			6" Dia. Canopy	10' Wire	1-6", 2-12"	1-100w Med.	OB
4161 OB	15" Dia.	12"			6" Dia. Canopy			3-75w Med.	OB
4162 OB	21" Dia.	28¾"			6" Dia. Canopy	12', 10'		3-100w Med.	OB
4166 OB	26" Dia.	24¾"			6" Dia. Canopy	6', 5'		6-100w Med.	OB
4167 OB	5" Dia.	8¼", 41¾" Max.*			6" Dia. Canopy	10' Wire	1-6", 2-12"	1-100w Med.	OB
4168 OB	32" Dia.	31"			6" Dia. Canopy	12', 10'		9-75w Med.	OB
5670 OB	5" W	10½"	6¾"	6½"	5" Dia. Back Plate			1-100w Med.	OB
4312 OB	½" Dia.	12" (stem for 4167 OB)							OB
4512 OB	⅝" Dia.	12" (stem for 4151 OB)							OB

*Maximum achievable height with stems included. Additional stems available, see above.

PLYMOUTH™

Classic never goes out of style. Plymouth's sweeping arms and vintage inspired candle sleeves with curved cast detailing are enhanced by the hand-rubbed Olde Bronze finish and light amber organza shade.

FINISH Olde Bronze GLASS Mocha-Colored
SHADE Light Amber Organza with Decorative Fabric Trim



Plymouth Bath,
page 391



4249 OB





4246 OB



4245 OB



4247 OB



4243 OB



4248 OB

PLYMOUTH Olde Bronze (OB)

ITEM	WIDTH/DIA.	HEIGHT	EXT.	DEPTH	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN	STEMS INCLUDED	BULBS	AVAILABLE FINISHES
4243 OB	18¼" Dia.	25¼"				5½" Dia. Canopy	6', 5'		3-60w Cand.	OB
4245 OB	34" W	22½"		18½"		4½" W, 8" L Canopy	6', 5'		6-60w Cand.	OB
4246 OB	27¾" Dia.	24¼"				5½" Dia. Canopy	6', 5'		6-60w Cand.	OB
4247 OB	6½" Dia.	10¾", 43" Max.*				5½" Dia. Canopy	10' Wire	1-6", 2-12"	1-100w Med.	OB
4248 OB	32¼" Dia.	31"				5½" Dia. Canopy	12', 10'		9-60w Cand.	OB
4249 OB	44½" Dia.	45"				5½" Dia. Canopy	12', 10'		15-40w Cand.	OB
4312 OB	½" Dia.	12" (stem)								OB

*Maximum achievable height with stems included. Additional stems available, see above.



4242 OB



4241 OB



5470 OB



4240 OB



4252 OB



4244 OB



PLYMOUTH Olde Bronze (OB)

ITEM	WIDTH/DIA.	HEIGHT	EXT.	DEPTH	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN	STEMS INCLUDED	BULBS	AVAILABLE FINISHES
4240 OB	6½" W	14"	7½"		8½"	4½" W, 9¼" H Back Plate			1-60w Cand.	OB
4241 OB	17½" Dia.	8¼"							3-60w Med.	OB
4242 OB	16" Dia.	12¼"				5½" Dia. Canopy			3-75w Med.	OB
4244 OB	24¾" Dia.	29¼"				5½" Dia. Canopy	12', 10'		3-75w Med.	OB
4252 OB	38½" W	23¼"		16"		4½" W, 8" L Canopy	6', 5'		2-100w Med.	OB
5470 OB	5½" W	9½"	7¾"		4¾"	4½" W, 9¼" H Back Plate			1-100w Med.	OB



4258 OB



4259 OB



4254 OB

PLYMOUTH Olde Bronze (OB)

ITEM	WIDTH/DIA.	HEIGHT	EXT.	DEPTH	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN	STEMS INCLUDED	BULBS	AVAILABLE FINISHES
4254 OB	17¾" Dia.	33½"				5½" Dia. Canopy	12', 10'		4-60w Cand.	OB
4258 OB	24" Dia.	43"				5½" Dia. Canopy	12', 10'		8-60w Cand.	OB
4259 OB	30" Dia.	55½"				5½" Dia. Canopy	12', 10'		9-60w Cand.	OB

CELLO™

Cello's bold updated traditional design has flowing and graceful bowed uprights in an Antique Bronze finish, with sophisticated antique highlights and a vintage faux alabaster glass.

FINISH Antique Bronze

GLASS Vintage Faux Alabaster



4569 AT





4561 AT



4564 AT



4563 AT



4567 AT



4566 AT



5450 AT



4568 AT

CELLO Antique Bronze (AT)

ITEM	WIDTH/DIA.	HEIGHT	EXT.	DEPTH	TOPTO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN	STEMS INCLUDED	BULBS	AVAILABLE FINISHES
4561 AT	19" Dia.	16"				6" Dia. Canopy			2-75w Med.	AT
4563 AT	22½" Dia.	21"				6" Dia. Canopy	6', 5'		3-100w Med.	AT
4564 AT	21" Dia.	25"				6" Dia. Canopy	12', 10'		3-100w Med.	AT
4566 AT	31¾" Dia.	24¾"				6" Dia. Canopy	6', 5'		6-100w Med.	AT
4567 AT	8½" Dia.	7", 40¾" Max.*				6" Dia. Canopy	10' Wire	1-6", 2-12"	1-100w Med.	AT
4568 AT	35¾" Dia.	32½"				6" Dia. Canopy	12', 10'		9-100w Med.	AT
4569 AT	47" Dia.	43"				6" Dia. Canopy	12', 10'		15-60w Med.	AT
5450 AT	8½" W	8¼"	8"		4"	4" W, 7" H Back Plate			1-100w Med.	AT
4312 AT	½" Dia.	12" (stem)								AT

*Maximum achievable height with stems included. Additional stems available, see above.

YORKTOWN™

The elegant Yorktown collection offers updated traditional styling with cast detailing for an authentic touch. Yorktown's tall candle sleeves, finials and ball transitions combine to make this classic design perfect for any décor.

FINISH Antique Nickel

CANDLE SLEEVES Antique Nickel or Off-White



Yorktown Bath,
pages 384-385



3628 AN



3620 AN



3623 AN



3622 AN



3625 AN

Antique Nickel Yorktown fixtures come with both Antique Nickel and off-white candle sleeves giving you the option to customize your look.



3626 AN

YORKTOWN Antique Nickel (AN)

ITEM	WIDTH/DIA.	HEIGHT	EXT.	DEPTH	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN	STEMS INCLUDED	BULBS	AVAILABLE FINISHES
3620 AN	4¾" W	13"	4¾"		8"	4¾" W, 9" H Back Plate			1-60w Cand.	AN, BR
3622 AN	13¾" W	15"	6½"		10½"	4¾" W, 9" H Back Plate			2-60w Cand.	AN, BR
3623 AN	20" Dia.	25"				6" Dia. Canopy	6', 5'		3-60w Cand.	AN, BR
3625 AN	24" Dia.	25"				6" Dia. Canopy	6', 5'		5-60w Cand.	AN, BR
3626 AN	28" Dia.	27"				6" Dia. Canopy	6', 5'		6-60w Cand.	AN, BR
3628 AN	32" Dia.	29"				6" Dia. Canopy	12', 10'		9-60w Cand.	AN, BR

YORKTOWN™

The elegant Yorktown collection offers updated traditional styling with cast detailing for an authentic touch. Yorktown's tall candle sleeves, finials and ball transitions combine to make this classic design perfect for any décor.

FINISH Brushed Bronze
CANDLE SLEEVES Antiqued



Yorktown Bath,
pages 384-385



3628 BR



3620 BR



3623 BR



3622 BR



3625 BR



3626 BR

YORKTOWN Brushed Bronze (BR)

ITEM	WIDTH/DIA.	HEIGHT	EXT.	DEPTH	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN	STEMS INCLUDED	BULBS	AVAILABLE FINISHES
3620 BR	4¾" W	13"	4¾"		8"	4¾" W, 9" H Back Plate			1-60w Cand.	AN, BR
3622 BR	13¾" W	15"	6½"		10½"	4¾" W, 9" H Back Plate			2-60w Cand.	AN, BR
3623 BR	20" Dia.	25"				6" Dia. Canopy	6', 5'		3-60w Cand.	AN, BR
3625 BR	24" Dia.	25"				6" Dia. Canopy	6', 5'		5-60w Cand.	AN, BR
3626 BR	28" Dia.	27"				6" Dia. Canopy	6', 5'		6-60w Cand.	AN, BR
3628 BR	32" Dia.	29"				6" Dia. Canopy	12', 10'		9-60w Cand.	AN, BR

LANDON™

Landon is a unique foyer lantern collection with an updated traditional chain hung design infused by cool, retro style. Its oversized rectangular framework enables the focus to be on elegant extended candle sleeves finished to match.

FINISH Brushed Nickel

GLASS Etched Opal (3017 BN only)



3015 BN



3014 BN



3013 BN



3017 BN

L A N D O N Brushed Nickel (BN)

ITEM	WIDTH/DIA.	HEIGHT	EXT.	DEPTH	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN	STEMS INCLUDED	BULBS	AVAILABLE FINISHES
3013 BN	15" Dia.	24½"				5½" Dia. Canopy	12', 10'		4-60w Cand.	BN
3014 BN	18" Dia.	28½"				5½" Dia. Canopy	12', 10'		4-60w Cand.	BN
3015 BN	24" Dia.	30"				5½" Dia. Canopy	12', 10'		5-60w Cand.	BN
3017 BN	8" Dia.	15", 48" Max.*				5½" Dia. Canopy	10' Wire	1-6", 2-12"	1-100w Med.	BN
4312 BN	½" Dia.	12" (stem)								BN


*Maximum achievable height with stems included. Additional stems available, see above.

WINGATE™

Wingate offers tradition with a twist. Clear, floating beveled glass panels surround understated cast round candle cups and candle sleeves, giving it a modern yet classic style.

FINISH Polished Antique Nickel

GLASS Clear Beveled Panels



Scan to view a video of the Wingate collection



3009 PL



3003 PL



3001 PL



3004 PL



3008 PL

WINGATE Polished Antique Nickel (PL)

ITEM	WIDTH/DIA.	HEIGHT	EXT.	DEPTH	TOPTO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN	STEMS INCLUDED	BULBS	AVAILABLE FINISHES
3001 PL	16" W	15¼"				5¼" Square Canopy			4-60w Cand.	OZ, PL
3003 PL	12" W	13"				5" Dia. Canopy			3-60w Cand.	OZ, PL
3004 PL	20" W	29"				5" Dia. Canopy	6', 5'		6-60w Cand.	OZ, PL
3008 PL	20" W	33½"				5" Dia. Canopy	12', 10'		6-60w Cand.	OZ, PL
3009 PL	26" W	43¼"				5" Dia. Canopy	12', 10'		8-60w Cand.	OZ, PL



3000 PL



3002 PL



3005 PL



3006 PL

WINGATE Polished Antique Nickel (PL)


ITEM	WIDTH/DIA.	HEIGHT	EXT.	DEPTH	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN	STEMS INCLUDED	BULBS	AVAILABLE FINISHES
3000 PL	12" W	21¼"				5" Dia. Canopy	6', 5'		4-60w Cand.	OZ, PL
3002 PL	10" W	12½"	5½"		6¾"	8" W, 11¼" H Back Plate			2-60w Cand.	OZ, PL
3005 PL	32" W	19¼"		20"		4½" W, 6½" L Canopy	6', 5'		10-60w Cand.	OZ, PL
3006 PL	16" W	28"				5" Dia. Canopy	6', 5'		4-60w Cand.	OZ, PL

Wingate offers tradition with a twist. Clear, floating beveled glass panels surround understated cast round candle cups and candle sleeves, giving it a modern yet classic style.

Oil Rubbed Bronze **FINISH**
Clear Beveled Panels **GLASS**

WINGATE™

Scan to view a video of
the Wingate collection



3009 OZ



3003 OZ



3001 OZ



3004 OZ



3008 OZ

WINGATE Oil Rubbed Bronze (OZ)

ITEM	WIDTH/DIA.	HEIGHT	EXT.	DEPTH	TOPTO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN	STEMS INCLUDED	BULBS	AVAILABLE FINISHES
3001 OZ	16" W	15¼"				5¼" Square Canopy			4-60w Cand.	OZ, PL
3003 OZ	12" W	13"				5" Dia. Canopy			3-60w Cand.	OZ, PL
3004 OZ	20" W	29"				5" Dia. Canopy	6', 5'		6-60w Cand.	OZ, PL
3008 OZ	20" W	33½"				5" Dia. Canopy	12', 10'		6-60w Cand.	OZ, PL
3009 OZ	26" W	43¼"				5" Dia. Canopy	12', 10'		8-60w Cand.	OZ, PL



3000 OZ



3002 OZ



3005 OZ



3006 OZ

WINGATE Oil Rubbed Bronze (OZ)

ITEM	WIDTH/DIA.	HEIGHT	EXT.	DEPTH	TOPTO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN	STEMS INCLUDED	BULBS	AVAILABLE FINISHES
3000 OZ	12" W	21¼"				5" Dia. Canopy	6', 5'		4-60w Cand.	OZ, PL
3002 OZ	10" W	12½"	5½"		6¾"	8" W, 11¼" H Back Plate			2-60w Cand.	OZ, PL
3005 OZ	32" W	19¼"		20"		4½" W, 6½" H Canopy	6', 5'		10-60w Cand.	OZ, PL
3006 OZ	16" W	28"				5" Dia. Canopy	6', 5'		4-60w Cand.	OZ, PL

GENTRY™

Gentry's traditional design is offered in two classic finishes, Pewter and Polished Brass. The clear bent glass panels, white candle sleeves and coordinating candle chasers add classic elegance to this timeless style.

FINISH Pewter
GLASS Clear Rounded Panels



3479 PW



3472 PW



3473 PW



3470 PW



3478 PW



3474 PW

GENTRY Pewter (PW)

ITEM	WIDTH/DIA.	HEIGHT	EXT.	DEPTH	TOPTO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN	STEMS INCLUDED	BULBS	AVAILABLE FINISHES
3470 PW	8" Dia.	12"				5½" Dia. Canopy	6', 5'		3-60w Cand.	PB, PW
3472 PW	9½" Dia.	9¼"							2-40w Cand.	PB, PW
3473 PW	11½" Dia.	9½"							3-40w Cand.	PB, PW
3474 PW	12" Dia.	20"				5½" Dia. Canopy	6', 5'		4-60w Cand.	PB, PW
3478 PW	14" Dia.	25"				5½" Dia. Canopy	12', 10'		6-60w Cand.	PB, PW
3479 PW	17" Dia.	41"				5½" Dia. Canopy	12', 10'		12-60w Cand.	PB, PW

GENTRY™

Gentry's traditional design is offered in two classic finishes, Pewter and Polished Brass. The clear bent glass panels, white candle sleeves and coordinating candle chasers add classic elegance to this timeless style.

FINISH Polished Brass

GLASS Clear Rounded Panels



3479 PB



3472 PB



3473 PB



3470 PB



3478 PB



3474 PB

GENTRY Polished Brass (PB)

ITEM	WIDTH/DIA.	HEIGHT	EXT.	DEPTH	TOPTO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN	STEMS INCLUDED	BULBS	AVAILABLE FINISHES
3470 PB	8" Dia.	12"				5½" Dia. Canopy	6', 5'		3-60w Cand.	PB, PW
3472 PB	9½" Dia.	9¼"							2-40w Cand.	PB, PW
3473 PB	11½" Dia.	9½"							3-40w Cand.	PB, PW
3474 PB	12" Dia.	20"				5½" Dia. Canopy	6', 5'		4-60w Cand.	PB, PW
3478 PB	14" Dia.	25"				5½" Dia. Canopy	12', 10'		6-60w Cand.	PB, PW
3479 PB	17" Dia.	41"				5½" Dia. Canopy	12', 10'		12-60w Cand.	PB, PW

CAMBRIDGE™

Cambridge offers classic New England appeal. The solid cast components, brass turnings, beaded ball fonts and clear optic glass reinforce its timeless style. Available in Pewter, Burnished Brass and Olde Bronze finishes.

FINISH Burnished Brass **GLASS** Clear Optic

SHADE Pleated Off-White Fabric (optional); 3610 BB Ivory Hardback Linen Fabric Shade Included



4419 BB





4412 BB
(shown with optional shade)



4415 BB



3610 BB
(shade included)



4421 OW
(optional shade)



4410 BB



4417 BB



4416 BB

CAMBRIDGE Burnished Brass (BB)

ITEM	WIDTH/DIA.	HEIGHT	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN	BULBS	AVAILABLE FINISHES
3610 BB	14½" W	18"	4"	14"	4¾" W, 7¾" H Back Plate		2-60w Cand.	BB, OB, PW
4410 BB	4½" W	11"	9½"	9¼"	4½" W, 6½" H Back Plate		1-60w Cand.	BB, OB, PW
4412 BB	15" W	11"	7"	9¼"	4½" W, 6½" H Back Plate		2-60w Cand.	BB, OB, PW
4415 BB	25" Dia.	26¼"			6¼" Dia. Canopy	6', 5'	5-60w Cand.	BB, OB, PW
4416 BB	28½" Dia.	26½"			6¼" Dia. Canopy	6', 5'	6-60w Cand.	BB, OB, PW
4417 BB	35½" Dia.	34½"			6¼" Dia. Canopy	12', 10'	15-40w Cand.	BB, OB, PW
4419 BB	48½" Dia.	46"			6¼" Dia. Canopy	12', 10'	25-25w Cand.	BB, OB, PW
4421 OW	5½" Dia.	5"					Do not exceed 40w	OW



4640 BB



3616 BB



3612 BB



4642 BB



3614 BB



3613 BB

CAMBRIDGE Burnished Brass (BB)

ITEM	WIDTH/DIA.	HEIGHT	EXT.	DEPTH	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN	STEMS INCLUDED	BULBS	AVAILABLE FINISHES
3612 BB	14½" Dia.	13"							3-60w Cand.	BB, OB, PW
3613 BB	21¼" Dia.	21", 22½"				6¾" Dia. Canopy	12', 10'		3-60w Cand.	BB, OB, PW
3614 BB	22½" Dia.	44½"				6¾" Dia. Canopy	12', 10'		3-60w Cand.	BB, OB, PW
3616 BB	16¼" Dia.	7½"							2-60w Med.	BB, OB, PW
4640 BB	4½" W	13"	9½"		9½"	4½" W, 6½" H Back Plate			1-60w Cand.	BB
4642 BB	14" W	13½"	8"		9"	4½" W, 6½" H Back Plate			2-60w Cand.	BB

*Height when hung with chain (includes loop).

Cambridge offers classic New England appeal. The solid cast components, brass turnings, beaded ball fonts and clear optic glass reinforce its timeless style.

Available in Pewter, Burnished Brass and Olde Bronze finishes.

CAMBRIDGE™

FINISH Olde Bronze GLASS Clear Optic

SHADE Pleated Off-White Fabric (optional); 3610 OB Ivory Hardback Linen Shade Included



4419 OB

50



4412 OB
(shown with optional shade)



4421 OW
(optional shade)



4410 OB



4416 OB



4417 OB



CAMBRIDGE Olde Bronze (OB)

ITEM	WIDTH/DIA.	HEIGHT	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN	BULBS	AVAILABLE FINISHES
4410 OB	4½"	11"	9½"	9¼"	4½" W, 6½" H Back Plate		1-60w Cand.	BB, OB, PW
4412 OB	15"	11"	7"	9¼"	4½" W, 6½" H Back Plate		2-60w Cand.	BB, OB, PW
4416 OB	28½"	26½"			6¼" Dia. Canopy	6', 5'	6-60w Cand.	BB, OB, PW
4417 OB	35½"	34½"			6¼" Dia. Canopy	12', 10'	15-40w Cand.	BB, OB, PW
4419 OB	48½" Dia.	46"			6¼" Dia. Canopy	12', 10'	25-25w Cand.	BB, OB, PW
4421 OW	5½" Dia.	5"					Do not exceed 40w	OW



3612 OB



3616 OB



3610 OB
(shade included)



4415 OB



3614 OB



3613 OB



CAMBRIDGE Olde Bronze (OB)

ITEM	WIDTH/DIA.	HEIGHT	EXT.	DEPTH	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN	STEMS INCLUDED	BULBS	AVAILABLE FINISHES
3610 OB	14½" W	18"	4"		14"	4¾" W, 7¾" H Back Plate			2-60w Cand.	BB, OB, PW
3612 OB	14½" Dia.	13"							3-60w Cand.	BB, OB, PW
3613 OB	21¼" Dia.	21", 22½"*				6¾" Dia. Canopy	12', 10'		3-60w Cand.	BB, OB, PW
3614 OB	22½" Dia.	44½"				6¾" Dia. Canopy	12', 10'		3-60w Cand.	BB, OB, PW
3616 OB	16¼" Dia.	7½"							2-60w Med.	BB, OB, PW
4415 OB	25"	26¼"				6¼" Dia. Canopy	6', 5'		5-60w Cand.	BB, OB, PW

*Height when hung with chain (includes loop).

CAMBRIDGE™

Cambridge offers classic New England appeal. The solid cast components, brass turnings, beaded ball fonts and clear optic glass reinforce its timeless style. Available in Pewter, Burnished Brass and Olde Bronze finishes.

FINISH Pewter GLASS Clear Optic

SHADE Optional Black Parchment with Gold Metallic Lining;
3610 PW Ivory Hardback Linen Fabric Shade Included



4419 PW





4412 PW
(shown with optional shade)



5122 BK
(optional shade)



4410 PW



4416 PW



4417 PW

50

CAMBRIDGE Pewter (PW)

ITEM	WIDTH/DIA.	HEIGHT	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN	BULBS	AVAILABLE FINISHES
4410 PW	4½" W	11"	9½"	9¼"	4½" W, 6½" H Back Plate		1-60w Cand.	BB, OB, PW
4412 PW	15" W	11"	7"	9¼"	4½" W, 6½" H Back Plate		2-60w Cand.	BB, OB, PW
4416 PW	28½" Dia.	26½"			6¼" Dia. Canopy	6', 5'	6-60w Cand.	BB, OB, PW
4417 PW	35½" Dia.	34½"			6¼" Dia. Canopy	12', 10'	15-40w Cand.	BB, OB, PW
4419 PW	48½" Dia.	46"			6¼" Dia. Canopy	12', 10'	25-25w Cand.	BB, OB, PW
5122 BK	5½" Dia.	5"					Do not exceed 40w	BK



3610 PW
(shade included)



3616 PW



3612 PW



3613 PW



3614 PW



4415 PW

CAMBRIDGE Pewter (PW)

ITEM	WIDTH/DIA.	HEIGHT	EXT.	DEPTH	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN	STEMS INCLUDED	BULBS	AVAILABLE FINISHES
3610 PW	14½" W	18"	4"		14"	4¾" W, 7¾" H Back Plate			2-60w Cand.	BB, OB, PW
3612 PW	14½" Dia.	13"							3-60w Cand.	BB, OB, PW
3613 PW	21¼" Dia.	21", 22½"				6¾" Dia. Canopy	12', 10'		3-60w Cand.	BB, OB, PW
3614 PW	22½" Dia.	44½"				6¾" Dia. Canopy	12', 10'		3-60w Cand.	BB, OB, PW
3616 PW	16¼" Dia.	7½"							2-60w Med.	BB, OB, PW
4415 PW	25" Dia.	26¼"				6¼" Dia. Canopy	6', 5'		5-60w Cand.	BB, OB, PW

*Height when hung with chain (includes loop).



IDEA

CENTER

VISIT US AT HINKLEYLIGHTING.COM FOR
MORE LIGHTING TIPS, DESIGNER IDEAS
AND STYLE GUIDES.

MODERN

TRADITIONAL

Striking the perfect balance between traditional and modern designs this style joins the best of both worlds, resulting in elegant, enduring collections that are chic and classic.

"THE RIGHT CHANDELIER CAN TAKE A ROOM FROM BEING GOOD TO BEING SPECTACULAR. IT'S OFTEN THE ICING ON THE CAKE."

RYAN KORBAN, RYAN KORBAN, NEW YORK CITY

ROCKFORD™

Rockford's bold traditional design features a cast urn centerpiece, candle chasers and beaded cast metal bobesches in a classic Forum Bronze finish. The clear seedy hurricane glass adds to its authentic appeal.

FINISH Forum Bronze

GLASS Clear Seedy Hurricane



4626 FB



3716 FB



3712 FB



4622 FB



4620 FB



3713 FB



3714 FB

ROCKFORD Forum Bronze (FB)

ITEM	WIDTH/DIA.	HEIGHT	EXT.	DEPTH	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN	STEMS INCLUDED	BULBS	AVAILABLE FINISHES
3712 FB	14½" Dia.	12¼"							3-60w Cand.	FB
3713 FB	20¾" Dia.	21", 24½**				6¾" Dia. Canopy	6', 5'		3-60w Cand.	FB
3714 FB	23" Dia.	42½"				6¾" Dia. Canopy	12', 10'		3-60w Cand.	FB
3716 FB	16¼" Dia.	7½"							2-60w Med.	FB
4620 FB	5" W	13"	9½"		8½"	4½" W, 6½" H Back Plate			1-60w Cand.	FB
4622 FB	14" W	13½"	7½"		9"	4½" W, 6½" H Back Plate			2-60w Cand.	FB
4626 FB	26¾" Dia.	29¼"				6¾" Dia. Canopy	6', 5'		6-60w Cand.	FB

*Height when hung with chain (includes loop).

VIRGINIAN™

Virginian captures a pure, classic elegance in either Pewter or Polished Brass finishes with a cast center column, round spun accents and white candle sleeves. Optional black parchment shades with gold metallic lining complete its grand presence.

FINISH Polished Brass

SHADE Optional Black Parchment with Gold Metallic Lining



5127 PB





5124 PB
(shown with optional shade)



5126 PB



5122 BK
(optional shade)



5120 PB



5128 PB



5129 PB

VIRGINIAN Polished Brass (PB)

ITEM	WIDTH/DIA.	HEIGHT	EXT.	DEPTH	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN	BULBS	AVAILABLE FINISHES
5120 PB	4¼" W	11"	7"		6"	4¼" W, 6" H Back Plate		1-60w Cand.*	PB, PW
5124 PB	11" W	11"	4½"		7"	4¼" W, 6" H Back Plate		2-60w Cand.*	PB, PW
5126 PB	22" Dia.	22"				5½" Dia. Canopy	6', 5'	6-60w Cand.	PB, PW
5127 PB	37" Dia.	44"				5½" Dia. Canopy	12', 10'	20-25w Cand.	PB, PW
5128 PB	30" Dia.	25"				5½" Dia. Canopy	6', 5'	8-60w Cand.	PB, PW
5129 PB	30" Dia.	34½"				5½" Dia. Canopy	12', 10'	12-60w Cand.	PB, PW
5122 BK	5½" Dia.	5"						Do not exceed 40w	BK

*Switched.

VIRGINIAN™

Virginian captures a pure, classic elegance in either Pewter or Polished Brass finishes with a cast center column, round spun accents and white candle sleeves. Optional black parchment shades with gold metallic lining complete its grand presence.

FINISH Pewter

SHADE Optional Black Parchment with Gold Metallic Lining



5127 PW





5124 PW



5126 PW
(shown with optional shade)



5122 BK
(optional shade)



5120 PW



5128 PW



5129 PW

VIRGINIAN Pewter (PW)

ITEM	WIDTH/DIA.	HEIGHT	EXT.	DEPTH	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN	BULBS	AVAILABLE FINISHES
5120 PW	4¼" W	11"	7"		6"	4¼" W, 6" H Back Plate		1-60w Cand.*	PB, PW
5124 PW	11" W	11"	4½"		7"	4¼" W, 6" H Back Plate		2-60w Cand.*	PB, PW
5126 PW	22" Dia.	22"				5½" Dia. Canopy	6', 5'	6-60w Cand.	PB, PW
5127 PW	37" Dia.	44"				5½" Dia. Canopy	12', 10'	20-25w Cand.	PB, PW
5128 PW	30" Dia.	25"				5½" Dia. Canopy	6', 5'	8-60w Cand.	PB, PW
5129 PW	30" Dia.	34½"				5½" Dia. Canopy	12', 10'	12-60w Cand.	PB, PW
5122 BK	5½" Dia.	5"						Do not exceed 40w	BK

*Switched.

PLANTATION™

A Hinkley classic, the ornate Plantation collection features exceptional pineapple shaped, clear optic glass that makes a noble statement with matching candle sleeves and elaborate, decorative cast detailing.

FINISH Polished Antique Nickel

GLASS Clear Optic SHADE Ivory Silk



Plantation Bath,
pages 400-401



Plantation Outdoor,
pages 610-614



4886 PL



4102 PL



5310 PL



4880 PL



4881 PL



5317 PL



4885 PL



4103 PL



2222 PL



PLANTATION Polished Antique Nickel (PL)

ITEM	WIDTH/DIA.	HEIGHT	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN	STEMS INCLUDED	BULBS	AVAILABLE FINISHES
2222 PL	12½" Dia.	28½"			6" Dia. Canopy	6', 5'		4-40w Cand.	BB, CB, PL, PZ
4102 PL	12" Dia.	8"						2-60w Med.	BB, CB, PL, PZ
4103 PL	13" Dia.	19"			6" Dia. Canopy	12', 10'		3-60w Cand.	BB, PL, PZ
4880 PL	6" W	15"	8¾"	10¾"	6" Dia. Back Plate			1-60w Cand.	BB, PL, PZ
4881 PL	16" Dia.	8¾"						3-60w Med.	BB, CB, PL, PZ
4885 PL	22" Dia.	24½"			6" Dia. Canopy	6', 5'		5-75w Med.	BB, PL, PZ
4886 PL	28" Dia.	33"			6" Dia. Canopy	6', 5'		7-60w Cand.**	BB, PL, PZ
5310 PL	5" W	8¾"	7"	5"	5" W, 8" H Back Plate			1-75w Med.	BB, PL, PZ
5317 PL	5" Dia.	8¼", 40¾" Max.*			6" Dia. Canopy	10' Wire	1-6", 2-12"	1-100w Med.	BB, PL, PZ
4312 PL	½" Dia.	12" (stem)							BB, PL, PZ

*Maximum achievable height with stems included. Additional stems available, see above. **Lighted center font, switched.

PLANTATION™

A Hinkley classic, the ornate Plantation collection features exceptional pineapple shaped, clear optic glass that makes a noble statement with matching candle sleeves and elaborate, decorative cast detailing.

FINISH Burnished Brass

GLASS Clear Optic SHADE Ivory Silk



Plantation Bath,
pages 400-401



Plantation Outdoor,
pages 610-614



4889 BB





4140 BB



4880 BB



5317 BB



4886 BB



4887 BB

50

PLANTATION Burnished Brass (BB)

ITEM	WIDTH/DIA.	HEIGHT	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN	STEMS INCLUDED	BULBS	AVAILABLE FINISHES
4140 BB	6" W	14½"	8½"	8½"	4¾" W, 12" H Back Plate			1-60w Cand.	BB, PZ
4880 BB	6" W	15"	8¾"	10¾"	6" Dia. Back Plate			1-60w Cand.	BB, PL, PZ
4886 BB	28" Dia.	33"			6" Dia. Canopy	6', 5'		7-60w Cand.**	BB, PL, PZ
4887 BB	33" Dia.	36¾"			6" Dia. Canopy	12', 10'		10-60w Cand.**	BB, PZ
4889 BB	56" Dia.	54"			6" Dia. Canopy	12', 10'		21-25w Cand., 1-25w Med.**	BB, PZ
5317 BB	5" Dia.	8¼", 40¾" Max.*			6" Dia. Canopy	10' Wire	1-6", 2-12"	1-100w Med.	BB, PL, PZ
4312 BB	½" Dia.	12" (stem)							BB, PL, PZ

*Maximum achievable height with stems included. Additional stems available, see above. **Lighted center font, switched.



4102 BB



4881 BB



5310 BB



4885 BB



4103 BB



2222 BB



PLANTATION Burnished Brass (BB)

ITEM	WIDTH/DIA.	HEIGHT	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN	STEMS INCLUDED	BULBS	AVAILABLE FINISHES
2222 BB	12½" Dia.	28½"			6" Dia. Canopy	6', 5'		4-40w Cand.	BB, CB, PL, PZ
4102 BB	12" Dia.	8"						2-60w Med.	BB, CB, PL, PZ
4103 BB	13" Dia.	19"			6" Dia. Canopy	12', 10"		3-60w Cand.	BB, PL, PZ
4881 BB	16" Dia.	8¾"						3-60w Med.	BB, CB, PL, PZ
4885 BB	22" Dia.	24½"			6" Dia. Canopy	6', 5'		5-75w Med.	BB, PL, PZ
5310 BB	5" W	8¾"	7"	5"	5" W, 8" H Back Plate			1-75w Med.	BB, PL, PZ

A Hinkley classic, the ornate Plantation collection features exceptional pineapple shaped, clear optic glass that makes a noble statement with matching candle sleeves and elaborate, decorative cast detailing.

Pearl Bronze FINISH
GLASS Clear Optic SHADE Ivory Silk

PLANTATION™



Plantation Bath,
pages 400-401



Plantation Outdoor,
pages 610-614



4889 PZ





5317 PZ



4140 PZ



4880 PZ



4886 PZ



4887 PZ



PLANTATION Pearl Bronze (PZ)

ITEM	WIDTH/DIA.	HEIGHT	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN	STEMS INCLUDED	BULBS	AVAILABLE FINISHES
4140 PZ	6" W	14½"	8½"	8½"	4¾" W, 12" H Back Plate			1-60w Cand.	BB, PZ
4880 PZ	6" W	15"	8¾"	10¾"	6" Dia. Back Plate			1-60w Cand.	BB, PL, PZ
4886 PZ	28" Dia.	33"			6" Dia. Canopy	6', 5'		7-60w Cand.**	BB, PL, PZ
4887 PZ	33" Dia.	36¾"			6" Dia. Canopy	12', 10'		10-60w Cand.**	BB, PZ
4889 PZ	56" Dia.	54"			6" Dia. Canopy	12', 10'		21-25w Cand., 1-25w Med.**	BB, PZ
5317 PZ	5" Dia.	8¼", 40¾" Max.*			6" Dia. Canopy	10' Wire	1-6", 2-12"	1-100w Med.	BB, PL, PZ
4312 PZ	½" Dia.	12" (stem)							BB, PL, PZ

*Maximum achievable height with stems included. Additional stems available, see above. **Lighted center font, switched.



5310 PZ



4881 PZ



4102 PZ



4885 PZ



4103 PZ



2222 PZ

PLANTATION Pearl Bronze (PZ)

ITEM	WIDTH/DIA.	HEIGHT	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN	STEMS INCLUDED	BULBS	AVAILABLE FINISHES
2222 PZ	12½" Dia.	28½"			6" Dia. Canopy	6', 5'		4-40w Cand.	BB, CB, PL, PZ
4102 PZ	12" Dia.	8"						2-60w Med.	BB, CB, PL, PZ
4103 PZ	13" Dia.	19"			6" Dia. Canopy	12', 10'		3-60w Cand.	BB, PL, PZ
4881 PZ	16" Dia.	8¾"						3-60w Med.	BB, CB, PL, PZ
4885 PZ	22" Dia.	24½"			6" Dia. Canopy	6', 5'		5-75w Med.	BB, PL, PZ
5310 PZ	5" W	8¾"	7"	5"	5" W, 8" H Back Plate			1-75w Med.	BB, PL, PZ

MARCELLINA™

Marcellina's grand style features beautiful, silver-highlighted cast leaf detailing, crystal bobesches, crystal ball finials and a large solid crystal center gazing ball. The Golden Bronze finish and optional damask silk shades add to the collection's luxurious sophistication.

FINISH Golden Bronze

SHADE Patterned Silk (optional)



4408 GR



4403 GR



4400 GR



4405 GR



4406 GR
(shown with optional shade)



4401 OW
(optional shade)



4404 GR

MARCELLINA Golden Bronze (GR)

ITEM	WIDTH/DIA.	HEIGHT	EXT.	DEPTH	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN	STEMS INCLUDED	BULBS	AVAILABLE FINISHES
4400 GR	6½" W	19"	6½"		7"	6½" W, 11¼" H Back Plate			1-60w Cand.	GR
4403 GR	15" Dia.	19¾"				6¼" Dia. Canopy	12', 10'		3-60w Cand.	GR
4404 GR	39" Dia.	42"				6¼" Dia. Canopy	12', 10'		8-60w Cand.	GR
4405 GR	25" Dia.	28"				6¼" Dia. Canopy	12', 10'		5-60w Cand.	GR
4406 GR	28½" Dia.	36"				6¼" Dia. Canopy	12', 10'		6-60w Cand.	GR
4408 GR	47" Dia.	53"				6¼" Dia. Canopy	12', 10'		15-60w Cand.	GR
4401 OW	5¾" Dia.	6½"							Do not exceed 40w	OW

CARLTON™

Carlton's elegant petite candelabra iron design, finished in authentic Silver Leaf, makes a sophisticated statement with luxurious amber pearl crystals, optional translucent organza shade and ornate details.

FINISH Silver Leaf

SHADE Organza (optional)



4779 SL

50



4775 SL



4771 SL
(shade included)



4774 SL



4772 SL



4776 SL
(shown with optional shade)



4770 SH
(optional shade)



4778 SL

CARLTON Silver Leaf (SL)

ITEM	WIDTH/DIA.	HEIGHT	EXT.	DEPTH	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN	STEMS INCLUDED	BULBS	AVAILABLE FINISHES
4771 SL	24" Dia.	17½"				7" Dia. Canopy			4-60w Cand.	SL
4772 SL	13½" W	19"	7"		9"	5" Dia. Back Plate			2-60w Cand.	SL
4774 SL	18" Dia.	22"				7" Dia. Canopy	6', 5'		4-60w Cand.	SL
4775 SL	24" Dia.	25"				7" Dia. Canopy	6', 5'		5-60w Cand.	SL
4776 SL	28" Dia.	28½"				7" Dia. Canopy	6', 5'		6-60w Cand.	SL
4778 SL	35" Dia.	36"				7" Dia. Canopy	12', 10'		12-60w Cand.	SL
4779 SL	45" Dia.	45½"				7" Dia. Canopy	12', 10'		21-40w Cand.	SL
4770 SH	4" Dia.	4¾"								SH

VERANDA™

Veranda is a regal design in wrought-iron construction and a hand-cracked bronze Summerstone finish. The clear crystal teardrop pendalogs and hand sewn silk shades add artisan details that redefine elegance.

FINISH Summerstone

GLASS Hand-Detail Veneto SHADE Hand-Sewn Silk



4899 SU





4801 SU



4806 SU



4893 SU



4802 SU



4809 SU



4807 SU



VERANDA Summerstone (SU)

ITEM	WIDTH/DIA.	HEIGHT	EXT.	DEPTH	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN	STEMS INCLUDED	BULBS	AVAILABLE FINISHES
4801 SU	20" Dia.	16"				6" Dia. Canopy			2-60w Med.	SU
4802 SU	14½" W	17¾"	8"		13¾"	4½" W, 8" H Back Plate			2-60w Cand.	SU
4806 SU	26" Dia.	29"				6" Dia. Canopy	6', 5'		5-60w Cand.	SU
4807 SU	46¾" Dia.	57"				8" Dia. Canopy	12', 10'		15-40w Cand.	SU
4809 SU	34¼" Dia.	46¾"				6" Dia. Canopy	12', 10'		9-60w Cand.	SU
4893 SU	12½" Dia.	15½"				6" Dia. Canopy	12', 10'		3-60w Cand.	SU
4899 SU	56" Dia.	70"				8" Dia. Canopy	12', 10'		16-40w Cand.	SU

PENDANT

perfection

IDEA

CENTER

VISIT US AT HINKLEYLIGHTING.COM FOR
MORE LIGHTING TIPS, DESIGNER IDEAS
AND STYLE GUIDES.



Create a state of suspended animation with posh pendants that add another design dimension to your space. Consider using a single pendant to complete a style statement while accomplishing task illumination over a desk or bedside table. Group a series together to illuminate a larger area such as a kitchen island or an entertaining area.

“I LIKE TO SEE PENDANTS GROUPED AT DIFFERENT HEIGHTS BUT CLOSE TOGETHER TO FEEL LIKE A CHANDELIER. I ALSO LOVE TO SEE PENDANTS HANGING SINGLY OVER A TASK AREA.”

CHRISTINA FLEUGGE, GREIGE DESIGN, SAN JOSE, CA

From Left: Fredrick Ramond's Pandora FR42407BRC, page 288; Zelda 3447 PN, page 055; Landon 3017 BN, page 169; Amelia 3124 CM, page 211; Amelia 3127 KZ, page 212; Shelter 1322 BK, page 455; Congress 3137 AN, page 214; Congress 3138 BC, page 222; Cordillera 4097 RI, page 105; Fredrick Ramond's Loft FR35013WAL, page 309; Fredrick Ramond's Zen FR46207BAM, page 305.

Amelia's classic pendant design reinvents vintage details with a cast glass fitter, cast metal trim ring and prominent hinges and clasps. The etched opal glass dome has an etched prismatic bottom lens for classic retro inspiration.

Chrome, Buckeye Bronze, Polished Antique Nickel FINISH
Etched Opal GLASS

AMELIA™



3127 CM



3124 CM

AMELIA Chrome (CM), Buckeye Bronze (BZ), Polished Antique Nickel (PL)

ITEM	WIDTH/DIA.	HEIGHT	EXT.	DEPTH	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN	STEMS INCLUDED	BULBS	AVAILABLE FINISHES
3124 CM, KZ, PL	12¾" W	13¾", 46¾" Max.*				5¼" Dia. Canopy	10' Wire	1-6", 2-12"	1-100w Med.	CM, KZ, PL
3127 CM, KZ, PL	11½" W	9¾", 42¾" Max.*				5¼" Dia. Canopy	10' Wire	1-6", 2-12"	1-100w Med.	CM, KZ, PL
4512 CM, KZ, PL	5/8" Dia.	12" (stem)								CM, KZ, PL

*Maximum achievable height with stems included. Additional stems available, see above.



3127 KZ



3124 KZ



3127 PL



3124 PL

AMELIA Chrome (CM), Buckeye Bronze (BZ), Polished Antique Nickel (PL)

ITEM	WIDTH/DIA.	HEIGHT	EXT.	DEPTH	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN	STEMS INCLUDED	BULBS	AVAILABLE FINISHES
3124 CM, KZ, PL	12¾" W	13¾", 46¾" Max.*				5¼" Dia. Canopy	10' Wire	1-6", 2-12"	1-100w Med.	CM, KZ, PL
3127 CM, KZ, PL	11½" W	9¾", 42¾" Max.*				5¼" Dia. Canopy	10' Wire	1-6", 2-12"	1-100w Med.	CM, KZ, PL
4512 CM, KZ, PL	5⅞" Dia.	12" (stem)								CM, KZ, PL

*Maximum achievable height with stems included. Additional stems available, see above.



Espresso Lab

- Espresso 12.00
- Espresso 14.00
- Espresso 16.00
- Espresso 18.00
- Espresso 20.00
- Espresso 22.00
- Espresso 24.00
- Espresso 26.00
- Espresso 28.00
- Espresso 30.00
- Espresso 32.00
- Espresso 34.00
- Espresso 36.00
- Espresso 38.00
- Espresso 40.00
- Espresso 42.00
- Espresso 44.00
- Espresso 46.00
- Espresso 48.00
- Espresso 50.00
- Espresso 52.00
- Espresso 54.00
- Espresso 56.00
- Espresso 58.00
- Espresso 60.00
- Espresso 62.00
- Espresso 64.00
- Espresso 66.00
- Espresso 68.00
- Espresso 70.00
- Espresso 72.00
- Espresso 74.00
- Espresso 76.00
- Espresso 78.00
- Espresso 80.00
- Espresso 82.00
- Espresso 84.00
- Espresso 86.00
- Espresso 88.00
- Espresso 90.00
- Espresso 92.00
- Espresso 94.00
- Espresso 96.00
- Espresso 98.00
- Espresso 100.00

Milk Lab

- Cold Green Smoothie 12.00
- Cold Green Smoothie 14.00
- Cold Green Smoothie 16.00
- Cold Green Smoothie 18.00
- Cold Green Smoothie 20.00
- Cold Green Smoothie 22.00
- Cold Green Smoothie 24.00
- Cold Green Smoothie 26.00
- Cold Green Smoothie 28.00
- Cold Green Smoothie 30.00
- Cold Green Smoothie 32.00
- Cold Green Smoothie 34.00
- Cold Green Smoothie 36.00
- Cold Green Smoothie 38.00
- Cold Green Smoothie 40.00
- Cold Green Smoothie 42.00
- Cold Green Smoothie 44.00
- Cold Green Smoothie 46.00
- Cold Green Smoothie 48.00
- Cold Green Smoothie 50.00
- Cold Green Smoothie 52.00
- Cold Green Smoothie 54.00
- Cold Green Smoothie 56.00
- Cold Green Smoothie 58.00
- Cold Green Smoothie 60.00
- Cold Green Smoothie 62.00
- Cold Green Smoothie 64.00
- Cold Green Smoothie 66.00
- Cold Green Smoothie 68.00
- Cold Green Smoothie 70.00
- Cold Green Smoothie 72.00
- Cold Green Smoothie 74.00
- Cold Green Smoothie 76.00
- Cold Green Smoothie 78.00
- Cold Green Smoothie 80.00
- Cold Green Smoothie 82.00
- Cold Green Smoothie 84.00
- Cold Green Smoothie 86.00
- Cold Green Smoothie 88.00
- Cold Green Smoothie 90.00
- Cold Green Smoothie 92.00
- Cold Green Smoothie 94.00
- Cold Green Smoothie 96.00
- Cold Green Smoothie 98.00
- Cold Green Smoothie 100.00

Tea Leads Hot Tea

- Tea Leads Hot Tea 12.00
- Tea Leads Hot Tea 14.00
- Tea Leads Hot Tea 16.00
- Tea Leads Hot Tea 18.00
- Tea Leads Hot Tea 20.00
- Tea Leads Hot Tea 22.00
- Tea Leads Hot Tea 24.00
- Tea Leads Hot Tea 26.00
- Tea Leads Hot Tea 28.00
- Tea Leads Hot Tea 30.00
- Tea Leads Hot Tea 32.00
- Tea Leads Hot Tea 34.00
- Tea Leads Hot Tea 36.00
- Tea Leads Hot Tea 38.00
- Tea Leads Hot Tea 40.00
- Tea Leads Hot Tea 42.00
- Tea Leads Hot Tea 44.00
- Tea Leads Hot Tea 46.00
- Tea Leads Hot Tea 48.00
- Tea Leads Hot Tea 50.00
- Tea Leads Hot Tea 52.00
- Tea Leads Hot Tea 54.00
- Tea Leads Hot Tea 56.00
- Tea Leads Hot Tea 58.00
- Tea Leads Hot Tea 60.00
- Tea Leads Hot Tea 62.00
- Tea Leads Hot Tea 64.00
- Tea Leads Hot Tea 66.00
- Tea Leads Hot Tea 68.00
- Tea Leads Hot Tea 70.00
- Tea Leads Hot Tea 72.00
- Tea Leads Hot Tea 74.00
- Tea Leads Hot Tea 76.00
- Tea Leads Hot Tea 78.00
- Tea Leads Hot Tea 80.00
- Tea Leads Hot Tea 82.00
- Tea Leads Hot Tea 84.00
- Tea Leads Hot Tea 86.00
- Tea Leads Hot Tea 88.00
- Tea Leads Hot Tea 90.00
- Tea Leads Hot Tea 92.00
- Tea Leads Hot Tea 94.00
- Tea Leads Hot Tea 96.00
- Tea Leads Hot Tea 98.00
- Tea Leads Hot Tea 100.00

Honeyuckle Gelato

- Honeyuckle Gelato 12.00
- Honeyuckle Gelato 14.00
- Honeyuckle Gelato 16.00
- Honeyuckle Gelato 18.00
- Honeyuckle Gelato 20.00
- Honeyuckle Gelato 22.00
- Honeyuckle Gelato 24.00
- Honeyuckle Gelato 26.00
- Honeyuckle Gelato 28.00
- Honeyuckle Gelato 30.00
- Honeyuckle Gelato 32.00
- Honeyuckle Gelato 34.00
- Honeyuckle Gelato 36.00
- Honeyuckle Gelato 38.00
- Honeyuckle Gelato 40.00
- Honeyuckle Gelato 42.00
- Honeyuckle Gelato 44.00
- Honeyuckle Gelato 46.00
- Honeyuckle Gelato 48.00
- Honeyuckle Gelato 50.00
- Honeyuckle Gelato 52.00
- Honeyuckle Gelato 54.00
- Honeyuckle Gelato 56.00
- Honeyuckle Gelato 58.00
- Honeyuckle Gelato 60.00
- Honeyuckle Gelato 62.00
- Honeyuckle Gelato 64.00
- Honeyuckle Gelato 66.00
- Honeyuckle Gelato 68.00
- Honeyuckle Gelato 70.00
- Honeyuckle Gelato 72.00
- Honeyuckle Gelato 74.00
- Honeyuckle Gelato 76.00
- Honeyuckle Gelato 78.00
- Honeyuckle Gelato 80.00
- Honeyuckle Gelato 82.00
- Honeyuckle Gelato 84.00
- Honeyuckle Gelato 86.00
- Honeyuckle Gelato 88.00
- Honeyuckle Gelato 90.00
- Honeyuckle Gelato 92.00
- Honeyuckle Gelato 94.00
- Honeyuckle Gelato 96.00
- Honeyuckle Gelato 98.00
- Honeyuckle Gelato 100.00

CONGRESS™

Congress is a traditional design that combines both hip and historical elements. This chic retro glass, mix and match collection comes in different shapes, colors and materials and is the perfect vintage accent to any décor.

FINISH Antique Nickel, Brushed Caramel, Chrome, Oil Rubbed Bronze

GLASS Etched Opal, Clear




3137 AN (shown), 3137 BC
3137 CM, 3137 OZ



3131 AN, 3131 BC (shown),
3131 CM, 3131 OZ



3137 AN, 3137 BC
3137 CM (shown), 3137 OZ



3131 AN, 3131 BC
3131 CM, 3131 OZ (shown)



3136 AN (shown), 3136 BC
3136 CM, 3136 OZ



3130 AN, 3130 BC (shown),
3130 CM, 3130 OZ



3130 AN, 3130 BC,
3130 CM (shown), 3130 OZ



3136 AN, 3136 BC, 3136 CM,
3136 OZ (shown)

C O N G R E S S Antique Nickel (AN), Brushed Caramel (BC), Chrome (CM), Oil Rubbed Bronze (OZ)

ITEM	WIDTH/DIA.	HEIGHT	BACK PLATE/CANOPY	WIRE/CHAIN	STEMS INCLUDED	BULBS	AVAILABLE FINISHES
3130 AN, BC, CM, OZ	8" Dia.	7", 39½" Max.*	4¾" Dia. Canopy	10' Wire	1-6", 2-12"	1-100w Med.	AN, BC, CM, OZ
3131 AN, BC, CM, OZ	12" Dia.	9¾", 42¼" Max.*	4¾" Dia. Canopy	10' Wire	1-6", 2-12"	1-100w Med.	AN, BC, CM, OZ
3136 AN, BC, CM, OZ	8" Dia.	7", 35½" Max.	4¾" Dia. Canopy	10' Wire	1-6", 2-12"	1-100w Med.	AN, BC, CM, OZ
3137 AN, BC, CM, OZ	12" Dia.	9¾", 42¼" Max.*	4¾" Dia. Canopy	10' Wire	1-6", 2-12"	1-100w Med.	AN, BC, CM, OZ
4312 AN, BC, CM, OZ	½" Dia.	12" (stem)					AN, BC, CM, OZ

*Maximum achievable height with stems included. Additional stems available, see above.



3128 AN (shown), 3128 BC,
3128 CM, 3128 OZ



3133 AN, 3133 BC (shown),
3133 CM, 3133 OZ



3129 AN (shown), 3129 BC,
3129 CM, 3129 OZ



3133 AN, 3133 BC,
3133 CM (shown), 3133 OZ



3128 AN, 3128 BC,
3128 CM, 3128 OZ (shown)



3134 AN, 3134 BC,
3134 CM (shown), 3134 OZ

C O N G R E S S Antique Nickel (AN), Brushed Caramel (BC), Chrome (CM), Oil Rubbed Bronze (OZ)

ITEM	WIDTH/DIA.	HEIGHT	BACK PLATE/CANOPY	WIRE/CHAIN	STEMS INCLUDED	BULBS	AVAILABLE FINISHES
3128 AN, BC, CM, OZ	7" Dia.	7", 39½", Max.*	4¾" Dia. Canopy	10' Wire	1-6", 2-12"	1-100w Med.	AN, BC, CM, OZ
3129 AN, BC, CM, OZ	8¾" Dia.	9", 41½" Max.*	4¾" Dia. Canopy	10' Wire	1-6", 2-12"	1-100w Med.	AN, BC, CM, OZ
3133 AN, BC, CM, OZ	7" Dia.	9¼", 41¾" Max.*	4¾" Dia. Canopy	10' Wire	1-6", 2-12"	1-100w Med.	AN, BC, CM, OZ
3134 AN, BC, CM, OZ	8¾" Dia.	9", 41½" Max.*	4¾" Dia. Canopy	10' Wire	1-6", 2-12"	1-100w Med.	AN, BC, CM, OZ
4312 AN, BC, CM, OZ	½" Dia.	12" (stem)					AN, BC, CM, OZ

*Maximum achievable height with stems included. Additional stems available, see above.



3134 AN, 3134 BC (shown),
3134 CM, 3134 OZ



3139 AN (shown), 3139 BC,
3139 CM, 3139 OZ



3135 AN, 3135 BC (shown),
3135 CM, 3135 OZ



3129 AN, 3129 BC,
3129 CM, 3129 OZ (shown)



3135 AN, 3135 BC,
3135 CM (shown), 3135 OZ



3139 AN, 3139 BC,
3139 CM, 3139 OZ (shown)

CONGRESS Antique Nickel (AN), Brushed Caramel (BC), Chrome (CM), Oil Rubbed Bronze (OZ)

ITEM	WIDTH/DIA.	HEIGHT	BACK PLATE/CANOPY	WIRE/CHAIN	STEMS INCLUDED	BULBS	AVAILABLE FINISHES
3129 AN, BC, CM, OZ	8¾" Dia.	9", 41½" Max.*	4¾" Dia. Canopy	10' Wire	1-6", 2-12"	1-100w Med.	AN, BC, CM, OZ
3134 AN, BC, CM, OZ	8¾" Dia.	9", 41½" Max.*	4¾" Dia. Canopy	10' Wire	1-6", 2-12"	1-100w Med.	AN, BC, CM, OZ
3135 AN, BC, CM, OZ	6" Dia.	10", 42½" Max.*	4¾" Dia. Canopy	10' Wire	1-6", 2-12"	1-100w Med.	AN, BC, CM, OZ
3139 AN, BC, CM, OZ	6" Dia.	10", 42½" Max.*	4¾" Dia. Canopy	10' Wire	1-6", 2-12"	1-100w Med.	AN, BC, CM, OZ
4312 AN, BC, CM, OZ	½" Dia.	12" (stem)					AN, BC, CM, OZ

*Maximum achievable height with stems included. Additional stems available, see above.



3141 AN (shown), 3141 BC,
3141 CM, 3141 OZ



3147 AN, 3147 BC (shown),
3147 CM, 3147 OZ



3146 AN, 3146 BC,
3146 CM (shown), 3146 OZ



3140 AN, 3140 BC,
3140 CM, 3140 OZ (shown)

CONGRESS Antique Nickel (AN), Brushed Caramel (BC), Chrome (CM), Oil Rubbed Bronze (OZ)

ITEM	WIDTH/DIA.	HEIGHT	EXT.	DEPTH	TOPTO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN	STEMS INCLUDED	BULBS	AVAILABLE FINISHES
3140 AN, BC, CM, OZ	8" Dia.	9½"				7" Dia. Canopy			1-100w Med.	AN, BC, CM, OZ
3141 AN, BC, CM, OZ	12" Dia.	11¾"				7" Dia. Canopy			1-100w Med.	AN, BC, CM, OZ
3146 AN, BC, CM, OZ	8" Dia.	9½"				7" Dia. Canopy			1-100w Med.	AN, BC, CM, OZ
3147 AN, BC, CM, OZ	12" Dia.	11¾"				7" Dia. Canopy			1-100w Med.	AN, BC, CM, OZ



3143 AN, 3143 BC,
3143 CM, 3143 OZ (shown)



3150 AN, 3150 BC,
3150 CM (shown), 3150 OZ



3145 AN, 3145 BC (shown),
3145 CM, 3145 OZ



3149 AN, 3149 BC,
3149 CM, 3149 OZ (shown)



3144 AN, 3144 BC,
3144 CM (shown), 3144 OZ



3151 AN, 3151 BC (shown),
3151 CM, 3151 OZ

C O N G R E S S Antique Nickel (AN), Brushed Caramel (BC), Chrome (CM), Oil Rubbed Bronze (OZ)

ITEM	WIDTH/DIA.	HEIGHT	EXT.	DEPTH	TOPTO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN	STEMS INCLUDED	BULBS	AVAILABLE FINISHES
3143 AN, BC, CM, OZ	7" Dia.	11¼"				7" Dia. Canopy			1-100w Med.	AN, BC, CM, OZ
3144 AN, BC, CM, OZ	8¾" Dia.	11"				7" Dia. Canopy			1-100w Med.	AN, BC, CM, OZ
3145 AN, BC, CM, OZ	6" Dia.	12"				7" Dia. Canopy			1-100w Med.	AN, BC, CM, OZ
3149 AN, BC, CM, OZ	7" Dia.	11¼"				7" Dia. Canopy			1-100w Med.	AN, BC, CM, OZ
3150 AN, BC, CM, OZ	8¾" Dia.	11"				7" Dia. Canopy			1-100w Med.	AN, BC, CM, OZ
3151 AN, BC, CM, OZ	6" Dia.	12"				7" Dia. Canopy			1-100w Med.	AN, BC, CM, OZ



3171 AN (clear)
3175 AN (white-shown)



3171 BC (clear)
3175 BC (white-shown)



3171 CM (clear-shown)
3175 CM (white)



3171 OZ (clear-shown)
3175 OZ (white)



3173 AN (white)
3174 AN (clear-shown)



3173 BC (white)
3174 BC (clear-shown)



3173 CM (white-shown)
3174 CM (clear)



3173 OZ (white-shown)
3174 OZ (clear)

C O N G R E S S Antique Nickel (AN), Brushed Caramel (BC), Chrome (CM), Oil Rubbed Bronze (OZ)

ITEM	WIDTH/DIA.	HEIGHT	EXT.	DEPTH	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN	STEMS INCLUDED	BULBS	AVAILABLE FINISHES
3171 AN, BC, CM, OZ	8¾" W	13"	10"		4¾"	4¾" Dia. Back Plate			1-100w Med.	AN, BC, CM, OZ
3173 AN, BC, CM, OZ	7" W	13½"	9¼"		4¾"	4¾" Dia. Back Plate			1-100w Med.	AN, BC, CM, OZ
3174 AN, BC, CM, OZ	7" W	13½"	9¼"		4¾"	4¾" Dia. Back Plate			1-100w Med.	AN, BC, CM, OZ
3175 AN, BC, CM, OZ	8¾" W	13"	10"		4¾"	4¾" Dia. Back Plate			1-100w Med.	AN, BC, CM, OZ



3170 AN (white-shown)
3176 AN (clear)



3170 BC (white-shown)
3176 BC (clear)



3170 CM (white)
3176 CM (clear-shown)



3170 OZ (white)
3176 OZ (clear-shown)



3172 AN (white)
3177 AN (clear-shown)



3172 BC (white)
3177 BC (clear-shown)



3172 CM (white-shown)
3177 CM (clear)



3172 OZ (white-shown)
3177 OZ (clear)

C O N G R E S S Antique Nickel (AN), Brushed Caramel (BC), Chrome (CM), Oil Rubbed Bronze (OZ)

ITEM	WIDTH/DIA.	HEIGHT	EXT.	DEPTH	TOPTO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN	STEMS INCLUDED	BULBS	AVAILABLE FINISHES
3170 AN, BC, CM, OZ	8" W	11¼"	9¾"	4¾"	4¾"	4¾" Dia. Back Plate			1-100w Med.	AN, BC, CM, OZ
3172 AN, BC, CM, OZ	6" W	14"	8¾"	4¾"	4¾"	4¾" Dia. Back Plate			1-100w Med.	AN, BC, CM, OZ
3176 AN, BC, CM, OZ	8" W	11¼"	9¾"	4¾"	4¾"	4¾" Dia. Back Plate			1-100w Med.	AN, BC, CM, OZ
3177 AN, BC, CM, OZ	6" W	14"	8¾"	4¾"	4¾"	4¾" Dia. Back Plate			1-100w Med.	AN, BC, CM, OZ



3138 AN



3138 BC



3138 CM



3138 OZ



3148 AN



3148 BC



3148 CM



3148 OZ



3178 AN



3178 BC



3178 CM



3178 OZ

C O N G R E S S Antique Nickel (AN), Brushed Caramel (BC), Chrome (CM), Oil Rubbed Bronze (OZ)

ITEM	WIDTH/DIA.	HEIGHT	EXT.	TOPTO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN	STEMS INCLUDED	BULBS	AVAILABLE FINISHES
3138 AN, BC, CM, OZ	9¾" Dia.	8½", 41" Max.*			4¾" Dia. Canopy	10' Wire	1-6", 2-12"	1-100w Med.	AN, BC, CM, OZ
3148 AN, BC, CM, OZ	10¾" Dia.	9¾"			7" Dia. Canopy			1-100w Med.	AN, BC, CM, OZ
3178 AN, BC, CM, OZ	9¾" W	12¾"	10½"	4¾"	4¾" Dia. Back Plate			1-100w Med.	AN, BC, CM, OZ
4312 AN, BC, CM, OZ	½" Dia.	12" (stem)							AN, BC, CM, OZ

*Maximum achievable height with stems included. Additional stems available, see above.





Gaining popularity as a chic alternative to chandeliers is the oversized flush mount ceiling fixture. This fixture can make a strong design statement, whether modern and minimalist or with all the glamour of a crystal-embellished design. Replacing your overhead lighting with a grand fixture of this scale can create a dramatic focal point in bedrooms, home offices, laundry rooms or any space where a traditionally-sized flush mount appears inadequate.

OVERSCALED SEMI-FLUSH

For additional Overscaled Semi-Flush options, see pages 226-235



BOLLA 4669 BN
Brushed Nickel | 23½" Dia., 16" H
*Also available in Brushed Bronze (BR)
and Olde Bronze (OB)*
Pages 108-119



CARLTON 4771 SL
Silver Leaf | 24" Dia., 17½" H
Page 207



CASA 4311 OL
Olde Black | 23" Dia., 14" H
Page 143



CIRRUS 3804 BN
Brushed Nickel | 20" Dia., 12" H
Page 99



CIRRUS 3805 BN
Brushed Nickel | 28" Dia., 12" H
Page 99



HAMPTON 3201 AN
Antique Nickel | 20" Dia., 12" H
Also available in Brushed Bronze (BR)
Pages 90-95



HAMPTON 3211 BR
Brushed Bronze | 26" Dia., 14½" H
Also available in Antique Nickel (AN)
Pages 90-95



HATHAWAY 3221 AN
Antique Nickel | 20¾" Dia., 12¾" H
Also available in Olde Bronze (OB)
Page 103



LAUREN 4061 VZ
Victorian Bronze | 20¾" Dia., 10½" H
Page 137



SLOAN 4543 RB
Venetian Bronze | 24" Dia., 14" H
Page 145



VALLEY 4702 BN
Brushed Nickel | 23" Dia., 13¾" H
Also available in Vintage Black (VK)
Pages 86-89



VERANDA 4801 SU
Summerstone | 20" Dia., 16" H
Page 209

HARPER™

Harper's sleek, retro design elevates the traditional flush mount with a unique opal glass bound by a prominent metal ring and decorative knobs available in three finishes.

FINISH Brushed Nickel, Chrome, Oil Rubbed Bronze

GLASS Etched Opal



3641 BN



3641 CM



3641 OZ

HARPER Brushed Nickel (BN), Chrome (CM), Oil Rubbed Bronze (OZ)

ITEM	WIDTH/DIA.	HEIGHT	EXT.	DEPTH	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN	STEMS INCLUDED	BULBS	AVAILABLE FINISHES
3641 BN	14½" Dia.	10"				7" Dia. Canopy			3-100w Med.	BN, CM, OZ
3641 CM	14½" Dia.	10"				7" Dia. Canopy			3-100w Med.	BN, CM, OZ
3641 OZ	14½" Dia.	10"				7" Dia. Canopy			3-100w Med.	BN, CM, OZ

PELHAM™

Pelham is a modern over scaled, semi flush mount collection with double floating arm construction. A chic alternative to the traditional chandelier, Pelham creates a dramatic focal point with its wide forged metal glass cradle.

FINISH Brushed Nickel, Brushed Bronze, Chrome, Oil Rubbed Bronze

GLASS Etched Opal

Side view of Pelham showing mounting strap



3821 BN



3821 BR



3821 CM



3821 OZ

PELHAM Brushed Nickel (BN), Brushed Bronze (BR), Chrome (CM), Oil Rubbed Bronze (OZ)

ITEM	WIDTH/DIA.	HEIGHT	EXT.	DEPTH	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN	STEMS INCLUDED	BULBS	AVAILABLE FINISHES
3821 BN	18¼" W	13¼"				6½" Dia. Canopy			3-100w Med.	BN, BR, CM, OZ
3821 BR	18¼" W	13¼"				6½" Dia. Canopy			3-100w Med.	BN, BR, CM, OZ
3821 CM	18¼" W	13¼"				6½" Dia. Canopy			3-100w Med.	BN, BR, CM, OZ
3821 OZ	18¼" W	13¼"				6½" Dia. Canopy			3-100w Med.	BN, BR, CM, OZ

HUTTON™

Hutton adds flair to the traditional semi-flush mount with its uniquely shaped opal glass shade, retro-inspired knurled knobs and robust arching arms available in three finishes.

FINISH Brushed Nickel, Chrome, Oil Rubbed Bronze

GLASS Etched Opal



3321 OZ



3321 BN



3321 CM

HUTTON Brushed Nickel (BN), Chrome (CM), Oil Rubbed Bronze (OZ)

ITEM	WIDTH/DIA.	HEIGHT	EXT.	DEPTH	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN	STEMS INCLUDED	BULBS	AVAILABLE FINISHES
3321 BN	16½" Dia.	10"				5¼" Dia. Canopy			3-100w Med.	BN, CM, OZ
3321 CM	16½" Dia.	10"				5¼" Dia. Canopy			3-100w Med.	BN, CM, OZ
3321 OZ	16½" Dia.	10"				5¼" Dia. Canopy			3-100w Med.	BN, CM, OZ

HADLEY™

The Hadley is a retro-styled collection available in four classic finish options: Antique Nickel, Brushed Bronze, Chrome and Oil Rubbed Bronze. The etched opal, one piece glass shade features a slim design that will complement a variety of decors.

FINISH Antique Nickel, Brushed Bronze, Chrome, Oil Rubbed Bronze

GLASS Etched Opal



3302 AN



3302 BR



3301 AN



3301 BR



3304 AN



3304 BR

HADLEY Antique Nickel (AN), Brushed Bronze (BR), Chrome (CM), Oil Rubbed Bronze (OZ)

ITEM	WIDTH/DIA.	HEIGHT	EXT.	DEPTH	TOPTO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN	STEMS INCLUDED	BULBS	AVAILABLE FINISHES
3301 AN	14" Dia.	5½"							3-60w Med.	AN, BR, CM, OZ
3302 AN	12" Dia.	4¾"							2-60w Med.	AN, BR, CM, OZ
3304 AN	20" Dia.	7¾"							4-100w Med.	AN, BR, CM, OZ
3301 BR	14" Dia.	5½"							3-60w Med.	AN, BR, CM, OZ
3302 BR	12" Dia.	4¾"							2-60w Med.	AN, BR, CM, OZ
3304 BR	20" Dia.	7¾"							4-100w Med.	AN, BR, CM, OZ



3302 CM



3302 OZ



3301 CM



3301 OZ



3304 CM



3304 OZ

HADLEY Antique Nickel (AN), Brushed Bronze (BR), Chrome (CM), Oil Rubbed Bronze (OZ)

ITEM	WIDTH/DIA.	HEIGHT	EXT.	DEPTH	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN	STEMS INCLUDED	BULBS	AVAILABLE FINISHES
3301 CM	14" Dia.	5½"							3-60w Med.	AN, BR, CM, OZ
3302 CM	12" Dia.	4¾"							2-60w Med.	AN, BR, CM, OZ
3304 CM	20" Dia.	7¾"							4-100w Med.	AN, BR, CM, OZ
3301 OZ	14" Dia.	5½"							3-60w Med.	AN, BR, CM, OZ
3302 OZ	12" Dia.	4¾"							2-60w Med.	AN, BR, CM, OZ
3304 OZ	20" Dia.	7¾"							4-100w Med.	AN, BR, CM, OZ

HADLEY™

The Hadley is a retro-styled collection available in four classic finish options: Antique Nickel, Brushed Bronze, Chrome and Oil Rubbed Bronze. The etched opal, one piece glass shade features a slim design that will complement a variety of decors.

FINISH Antique Nickel, Brushed Bronze, Chrome, Oil Rubbed Bronze

GLASS Etched Opal



3305 AN



3305 BR



3305 CM



3305 OZ

HADLEY Antique Nickel (AN), Brushed Bronze (BR), Chrome (CM), Oil Rubbed Bronze (OZ)

ITEM	WIDTH/DIA.	HEIGHT	EXT.	DEPTH	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE/CHAIN	STEMS INCLUDED	BULBS	AVAILABLE FINISHES
3305 AN	20" Dia.	21", 59¾" Max.*				6½" Dia. Canopy	10' Wire	2-6", 2-12"	4-100w Med.	AN, BR, CM, OZ
3305 BR	20" Dia.	21", 59¾" Max.*				6½" Dia. Canopy	10' Wire	2-6", 2-12"	4-100w Med.	AN, BR, CM, OZ
3305 CM	20" Dia.	21", 59¾" Max.*				6½" Dia. Canopy	10' Wire	2-6", 2-12"	4-100w Med.	AN, BR, CM, OZ
3305 OZ	20" Dia.	21", 59¾" Max.*				6½" Dia. Canopy	10' Wire	2-6", 2-12"	4-100w Med.	AN, BR, CM, OZ
6066 AN, BR, CM, OZ	5⅝" Dia.									AN, BR, CM, OZ

*Maximum achievable height with stems included. Additional stems available, see above.