



LED QUICK REFERENCE GUIDE

See pages 22 & 23 for our LED
PAR/Reflector and A lamp guide

DIMENSION™ LED LAMPS

Dimension™ warm tone dimming LED lamps

Applications/Features

- Indoor residential and commercial lighting
- Down lighting
- Display lighting
- Accent lighting
- Dims from 2700K to 2200K

Dimension Warm Tone Dimming lamps feature an on-board "Direct Drive" integrated circuit with a microprocessor chip. This "Smart" chip manages the path of current which changes the CCT from 2700K down to 2200K.


This new generation of LED lamp technology has been tested with a wide assortment of dimmers and this list (shown left) reflects the ones we have selected to deliver the best overall dimming experience, while reaching the lowest dim level and lowest possible color temperature.

RECOMMENDED DIMMERS

Manufacturer	Model No.
Lutron	SLV600P MAGNETIC LOW VOLTAGE
Lutron	CT-603PGH ECO DIM INCANDESCENT
Lutron	DV600PR DIVA INCANDESCENT
Leviton	6674 UNIVERSAL LED
Cooper	DLC03P LED

Maximum number of lamps per dimmer = 10

Dims to warmer color like an incandescent




S9073
R20



S9025
R30



S9101
R40



Dimension Warm Tone Dimming LED Lamps

Item Number	Lamp Description	Watts	Volts	CRI	CCT	Lumens	Beam	M.O.L. (Inches)	Life/Hours
S9073	7.8R20/LED/2700K	7.8	120	80	2700K	460	108°	3 7/8	30,000
S9025	12.8R30/LED/2700K	12.8	120	80	2700K	750	108°	5 1/4	40,000
S9101	16R40/LED/2700K	16	120	80	2700K	1000	108°	6 3/8	30,000

Consult Satco or visit www.satco.com for an up to date dimmer compatibility list.

S9073 Pack: Master 24 / Inner 6/1
Pack: Master 12 / Inner 6/1




OMNI^X LED LAMPS

KolourOne Omni^X 10.5W A19 Omni-Directional[®] LED lamps

Applications / Features

- 60W A19 replacement
- Indoor residential and commercial lighting
- Down lighting
- Display lighting
- Table lamps
- Pendants
- Dimmable



KolourOne Omni^X 10.5W A19 Omni-Directional LED Lamps



omni^X
360° ILLUMINATION

KolourOne[™]
LED TECHNOLOGY

Item Number	Lamp Description	Watts	Volts	CRI	CCT	Lumens	Beam	M.O.L. (Inches)	Life/Hours	Pack
S9037*	10.5A19/OMNI/LED/2700K	10.5	120	84	2700K	810	360°	4 1/2	25,000	24/6
S9038*	10.5A19/OMNI/LED/3500K	10.5	120	83	3500K	830	360°	4 1/2	25,000	24/6
S9039	10.5A19/OMNI/LED/5000K	10.5	120	83	5000K	870	360°	4 1/2	25,000	24/6


* ENERGY STAR certified.

Pack: Master 24 / Inner 6/1

KolourOne Omni^X 11W A19 Omni-Directional[®] LED lamp, GU24 base

Applications / Features

- 60W A19 replacement
- Indoor residential and commercial lighting
- Down lighting
- Display lighting
- Table lamps
- Pendants
- Dimmable



KolourOne Omni^X 11W A19 Omni-Directional LED Lamps



omni^X
360° ILLUMINATION

KolourOne[™]
LED TECHNOLOGY

Item Number	Lamp Description	Watts	Volts	CRI	CCT	Lumens	Beam	M.O.L. (Inches)	Life/Hours	Pack
S9070	11A19/OMNI/LED/2700K/GU24	11	120	85	2700K	809	360°	4 1/2	25,000	24/6

Pack: Master 24 / Inner 6/1


MULTI-DIRECTIONAL LED LAMPS

Omni 300° LED lamps

Applications / Features

- Indoor residential and commercial lighting
- Down lighting
- Display lighting
- Accent lighting
- Direct replacement for 40 – 60 Watt incandescent lamps, uses only 7.6 – 9.8 Watts
- Dimmable

Available April 2015



Omni-directional LED lamps

Item Number	Lamp Description	Watts	Volts	CRI	CCT	Lumens	Beam	M.O.L. (Inches)	Life/Hours	Pack
S9212*	7.6A19/OMNI/300/LED/27K	7.6	120	80	2700K	460	300°	4 ½	25,000	24/6
S9213*	7.6A19/OMNI/300/LED/35K	7.6	120	80	3500K	480	300°	4 ½	25,000	24/6
S9214*	7.6A19/OMNI/300/LED/40K	7.6	120	80	4000K	490	300°	4 ½	25,000	24/6
S9215*	7.6A19/OMNI/300/LED/50K	7.6	120	80	5000K	510	300°	4 ½	25,000	24/6
S9208*	9.8A19/OMNI/300/LED/27K	9.8	120	80	2700K	810	300°	4 ½	25,000	24/6
S9209*	9.8A19/OMNI/300/LED/35K	9.8	120	80	3500K	850	300°	4 ½	25,000	24/6
S9210*	9.8A19/OMNI/300/LED/40K	9.8	120	80	4000K	870	300°	4 ½	25,000	24/6
S9211*	9.8A19/OMNI/300/LED/50K	9.8	120	80	5000K	900	300°	4 ½	25,000	24/6
S9216*	9.8A19/OMNI/300/LED/27K/GU24	9.8	120	80	2700K	810	300°	4 ½	25,000	24/6


* ENERGY STAR pending - April 2015

Pack: Master 24 / Inner 6/1

Multi-directional dimmable & non-dimmable A19 LED lamps

Applications / Features

- Indoor residential and commercial lighting
- Pendants
- Display lighting
- Accent lighting
- 7W and 6.4W replaces 40W
- 10W and 9.6W replaces 60W



Multi-directional Dimmable A19 LED Lamps

Item Number	Lamp Description	Watts	Volts	CRI	CCT	Lumens	Beam	M.O.L. (Inches)	Life/Hours	Pack
S9107	7A19/LED/27K/450L	7	120	80	2700K	450	215°	4 ⅝	25,000	24/6
S9108	7A19/LED/50K/510L	7	120	80	5000K	510	215°	4 ⅝	25,000	24/6
S9109	10A19/LED/27K/800L	10	120	80	2700K	800	215°	4 ⅝	25,000	24/6
S9110	10A19/LED/50K/900L	10	120	80	5000K	900	215°	4 ⅝	25,000	24/6
S9111	10A19/LED/27K/GU24/800L	10	120	80	2700K	800	215°	4 ⅝	25,000	24/6

Multi-directional Non-dimmable A19 LED Lamps

Item Number	Lamp Description	Watts	Volts	CRI	CCT	Lumens	Beam	M.O.L. (Inches)	Life/Hours	Pack
S9112	6.4A19/LED/2700K/120V	6.4	120	80	2700K	470	240°	4 ¼	25,000	24/6
S9113	6.4A19/LED/5000K/120V	6.4	120	80	5000K	500	240°	4 ¼	25,000	24/6
S9114	9.6A19/LED/2700K/120V	9.6	120	80	2700K	810	240°	4 ⅝	25,000	24/6
S9115	9.6A19/LED/5000K/120V	9.6	120	80	5000K	850	240°	4 ⅝	25,000	24/6



Pack: Master 24 / Inner 6/1

PANEL ARRAY 2.0 LED LAMPS

KolourOne Panel Array 2.0 7W PAR20 LED lamps

Applications / Features

- Indoor residential and commercial lighting
- Entertainment lighting
- Down lighting
- Display lighting
- Accent lighting
- Dimmable



KolourOne Panel Array 2.0 LED PAR20 Lamps



Item Number	Lamp Description	Watts	Volts	CRI	CCT	Lumens	Beam	M.O.L. (Inches)	Life/Hours	Pack
S8921*	7PAR20/LED/40/2700K/PA 2.0	7	120	84	2700K	420	40°	3 7/16	35,000	24/6
S8922*	7PAR20/LED/40/3500K/PA 2.0	7	120	83	3500K	435	40°	3 7/16	35,000	24/6
S8923	7PAR20/LED/40/5000K/PA 2.0	7	120	83	5000K	455	40°	3 7/16	35,000	24/6





* ENERGY STAR certified.

Pack: Master 24 / Inner 6/1

KolourOne Panel Array 2.0 14W PAR30 short neck LED lamps

Applications / Features

- Indoor residential and commercial lighting
- Down lighting
- Display lighting
- Accent lighting
- Dimmable



KolourOne Panel Array 2.0 LED PAR30 Short Neck Lamps



Item Number	Lamp Description	Watts	Volts	CRI	CCT	Lumens	Beam	M.O.L. (Inches)	Life/Hours	Pack
S8934*	14PAR30SN/LED/40/2700K/PA2.0	14	120	84	2700K	860	40°	3 5/8	35,000	12/6
S8935*	14PAR30SN/LED/40/3500K/PA2.0	14	120	83	3500K	890	40°	3 5/8	35,000	12/6
S8936	14PAR30SN/LED/40/5000K/PA2.0	14	120	83	5000K	930	40°	3 5/8	35,000	12/6
S8941*	14PAR30SN/LED/60/2700K/PA2.0	14	120	84	2700K	860	60°	3 5/8	35,000	12/6
S8942*	14PAR30SN/LED/60/3500K/PA2.0	14	120	83	3500K	890	60°	3 5/8	35,000	12/6
S8943	14PAR30SN/LED/60/5000K/PA2.0	14	120	83	5000K	930	60°	3 5/8	35,000	12/6

* ENERGY STAR certified.


Pack: Master 12 / Inner 6/1

PANEL ARRAY 2.0 LED LAMPS

KolourOne Panel Array 2.0 14W PAR30 long neck LED lamps

Applications / Features

- Indoor residential and commercial lighting
- Down lighting
- Display lighting
- Accent lighting
- Dimmable



KolourOne Panel Array 2.0 LED PAR30 Long Neck Lamps



Item Number	Lamp Description	Watts	Volts	CRI	CCT	Lumens	Beam	M.O.L. (Inches)	Life/Hours	Pack
S8947*	14PAR30LN/LED/40/2700K/PA2.0	14	120	84	2700K	860	40°	4 ½	35,000	12/6
S8948*	14PAR30LN/LED/40/3500K/PA2.0	14	120	83	3500K	890	40°	4 ½	35,000	12/6
S8949	14PAR30LN/LED/40/5000K/PA2.0	14	120	83	5000K	930	40°	4 ½	35,000	12/6
S8971*	14PAR30LN/LED/60/2700K/PA2.0	14	120	84	2700K	860	60°	4 ½	35,000	12/6
S8972*	14PAR30LN/LED/60/3500K/PA2.0	14	120	83	3500K	890	60°	4 ½	35,000	12/6
S8973	14PAR30LN/LED/60/5000K/PA2.0	14	120	83	5000K	930	60°	4 ½	35,000	12/6


* ENERGY STAR certified.

Pack: Master 12 / Inner 6/1

KolourOne Panel Array 2.0 14W PAR30 long neck LED lamp, GU24 base

Applications / Features

- Indoor residential and commercial lighting
- Down lighting
- Display lighting
- Accent lighting
- Dimmable



KolourOne Panel Array 2.0 LED PAR30 Long Neck Lamp, GU24 Base



Item Number	Lamp Description	Watts	Volts	CRI	CCT	Lumens	Beam	M.O.L. (Inches)	Life/Hours	Pack
S9054	14PAR30LN/LED/40/2700K/GU24	14	120	84	2700K	860	40°	4 ½	25,000	12/6


Pack: Master 12 / Inner 6/1

PANEL ARRAY 2.0 LED LAMPS

KolourOne Panel Array 2.0 17W PAR38 LED lamps

Applications / Features

- Indoor residential and commercial lighting
- Entertainment lighting
- Down lighting
- Display lighting
- Accent lighting
- Dimmable



KolourOne Panel Array 2.0 LED PAR38 Lamps



Item Number	Lamp Description	Watts	Volts	CRI	CCT	Lumens	Beam	M.O.L. (Inches)	Life/Hours	Pack
S8977*	17PAR38/LED/40/2700K/PA 2.0	17	120	84	2700K	1120	40°	5 1/8	35,000	12/6
S8978*	17PAR38/LED/40/3500K/PA 2.0	17	120	83	3500K	1160	40°	5 1/8	35,000	12/6
S8979	17PAR38/LED/40/5000K/PA 2.0	17	120	83	5000K	1210	40°	5 1/8	35,000	12/6
S8984*	17PAR38/LED/60/2700K/PA 2.0	17	120	84	2700K	1120	60°	5 1/8	35,000	12/6
S8985*	17PAR38/LED/60/3500K/PA 2.0	17	120	83	3500K	1160	60°	5 1/8	35,000	12/6
S8986	17PAR38/LED/60/5000K/PA 2.0	17	120	83	5000K	1210	60°	5 1/8	35,000	12/6


* ENERGY STAR certified.

Pack: Master 12 / Inner 6/1

KolourOne Panel Array 2.0 17W PAR38 LED lamp, GU24 base

Applications / Features

- Indoor residential and commercial lighting
- Down lighting
- Display lighting
- Accent lighting
- Dimmable



KolourOne Panel Array 2.0 LED PAR38 Lamp, GU24 Base



Item Number	Lamp Description	Watts	Volts	CRI	CCT	Lumens	Beam	M.O.L. (Inches)	Life/Hours	Pack
S9060	17PAR38/LED/40/2700K/GU24	17	120	84	2700K	1120	40°	5	25,000	12/6



Pack: Master 12 / Inner 6/1

INDOOR/OUTDOOR LED PAR LAMPS

Indoor/Outdoor KolourOne Duo™ 7W PAR20 LED lamp

Applications / Features

- Indoor residential and commercial lighting
- Outdoor security and landscape lighting
- Down lighting
- Display lighting
- Accent lighting
- Dimmable
- IP65 rated



KolourOne Duo PAR20 Indoor/Outdoor LED Lamp





Item Number	Lamp Description	Watts	Volts	CRI	CCT	Lumens	Beam	M.O.L. (Inches)	Life/Hours	Pack
S9014	7PAR20/LED/40/3500K/IP65	7	120	83	3500K	400	40°	3 7/16	25,000	24/6

Pack: Master 24 / Inner 6/1

Indoor/Outdoor KolourOne Duo™ 13W PAR30 short neck LED lamp

Applications / Features

- Indoor residential and commercial lighting
- Outdoor security and landscape lighting
- Down lighting
- Display lighting
- Accent lighting
- Dimmable
- IP65 rated



KolourOne Duo PAR30 Short Neck Indoor/Outdoor LED Lamp



Item Number	Lamp Description	Watts	Volts	CRI	CCT	Lumens	Beam	M.O.L. (Inches)	Life/Hours	Pack
S9017	13PAR30SN/LED/40/3500K/IP65	13	120	83	3500K	820	40°	3 5/8	25,000	12/6


Pack: Master 12 / Inner 6/1

INDOOR/OUTDOOR LED PAR LAMPS

Indoor/Outdoor KolourOne Duo™ 13W PAR30 long neck LED lamp


Applications / Features

- Indoor residential and commercial lighting
- Outdoor security and landscape lighting
- Down lighting
- Display lighting
- Accent lighting
- Dimmable
- IP65 rated



Beam Angle: 40°

Illumination



Beam Angle: 40°

KolourOne Duo PAR30 Long Neck Indoor/Outdoor LED Lamp




Item Number	Lamp Description	Watts	Volts	CRI	CCT	Lumens	Beam	M.O.L. (Inches)	Life/Hours	Pack
S9020	13PAR30LN/LED/40/3500K/IP65	13	120	83	3500K	820	40°	3 1/2	25,000	12/6

Pack: Master 12 / Inner 6/1

Indoor/Outdoor KolourOne Duo™ 17W PAR38 LED lamp


Applications / Features

- Indoor residential and commercial lighting
- Outdoor security and landscape lighting
- Down lighting
- Display lighting
- Accent lighting
- Dimmable
- IP65 rated



Beam Angle: 40°

Illumination



Beam Angle: 40°

KolourOne Duo PAR38 Indoor/Outdoor LED Lamp



Item Number	Lamp Description	Watts	Volts	CRI	CCT	Lumens	Beam	M.O.L. (Inches)	Life/Hours	Pack
S9023	17PAR38/LED/40/3500K/IP65	17	120	83	3500K	1130	40°	5 1/8	25,000	12/6

Pack: Master 12 / Inner 6/1


LED REFLECTOR LAMPS

Ditto™ LED reflector lamps

Same R20 shape.
Even more efficient.

Applications / Features

- Down lighting
- Accent lighting
- Dimmable
- 45R20 replacement
- Damp location



Ditto R20 LED Reflector Lamps

Item Number	Lamp Description	Watts	Replaces	CRI	CCT	Lumens	Beam	M.O.L. (Inches)	Life/Hours	Pack
S9140	7R20/LED/27K/525L	7	S9040	80↑	2700K	525	106°	3 1/16	25,000	24/6
S9141	7R20/LED/30K/540L	7	S9002	80↑	3000K	540	106°	3 1/16	25,000	24/6
S9142	7R20/LED/40K/560L	7	S9041	80↑	4000K	560	106°	3 1/16	25,000	24/6
S9143	7R20/LED/50K/580L	7	S9042	80↑	5000K	580	106°	3 1/16	25,000	24/6


Pack: Master 24 / Inner 6/1

Ditto™ LED reflector lamps

Same BR30 shape.
Even more efficient.

Applications / Features

- Down lighting
- Accent lighting
- Dimmable
- 65BR30 replacement
- Damp location



Ditto BR30 LED Reflector Lamps

Item Number	Lamp Description	Watts	Volts	CRI	CCT	Lumens	Beam	M.O.L. (Inches)	Life/Hours	Pack
S9138	10BR30/LED/2700K/670L/120V	10	120	90	2700K	670	108°	5 3/16	25,000	12/6
S9139	10BR30/LED/2700K/GU24/670L/120V	10	120	90	2700K	670	108°	5	25,000	12/6
S9133	10BR30/LED/2700K/120V	10	120	80	2700K	750	108°	5 3/16	25,000	12/6
S9134	10BR30/LED/3000K/120V	10	120	80	3000K	800	108°	5 3/16	25,000	12/6
S9135	10BR30/LED/4000K/120V	10	120	80	4000K	830	108°	5 3/16	25,000	12/6
S9136	10BR30/LED/5000K/120V	10	120	80	5000K	860	108°	5 3/16	25,000	12/6
S9137	10BR30/LED/2700K/GU24/750L/120V	10	120	80	2700K	750	108°	4 1/2	25,000	12/6

Pack: Master 12 / Inner 6/1



LED REFLECTOR LAMPS

Ditto™ LED reflector lamps

Same R40 shape.
Even more efficient.

Applications / Features

- Down lighting
- Accent lighting
- Dimmable
- 65W and 85W BR40 replacement
- Damp location



Ditto R40 LED Reflector Lamps



Item Number	Lamp Description	Watts	Replaces	CRI	CCT	Lumens	Beam	M.O.L. (Inches)	Life/Hours	Pack
S9144	12BR40/LED/27K/900L	12	S9046	80↑	2700K	900	105°	6 ½	25,000	12/6
S9145	12BR40/LED/30K/930L	12	S9003	80↑	3000K	930	105°	6 ½	25,000	12/6
S9146	12BR40/LED/40K/970L	12	S9047	80↑	4000K	970	105°	6 ½	25,000	12/6
S9147	12BR40/LED/50K/1000L	12	S9048	80↑	5000K	1000	105°	6 ½	25,000	12/6
S9180	17BR40/LED/27K/1200L	17	S9049	80↑	2700K	1200	105°	6 ½	25,000	12/6
S9181	17BR40/LED/30K/1230L	17	S9006	80↑	3000K	1230	105°	6 ½	25,000	12/6
S9182	17BR40/LED/40K/1280L	17	S9050	80↑	4000K	1280	105°	6 ½	25,000	12/6
S9183	17BR40/LED/50K/1320L	17	S9051	80↑	5000K	1320	105°	6 ½	25,000	12/6

Pack: Master 12 / Inner 6/1

New Satco LED 8.5W BR30 Ditto

Equal in efficiency,
even greater value,
now in prepack displays

Applications / Features

- Indoor residential and commercial lighting
- 65W replacement
- 2700K
- Damp location



2 Pack displays,
24-2pks

Single pack displays,
48 lamps

8.5W BR30 LED Reflector Display Packs



Item Number	Lamp Description	Watts	Volts	CRI	CCT	Lumens	Base Type	M.O.L. (Inches)	Life/Hours	Pack/Master
S9148	8.5BR30/LED/2700K/650L/120V/D	8.5	120	80	2700K	650	E26	5 ¾	25,000	48
S9149	8.5BR30/LED/2700K/650L/120V/D/2PK	8.5	120	80	2700K	650	E26	5 ¾	25,000	24-2pks

*Consult Satco or visit www.satco.com for an up to date dimmer compatibility list.

**See separate warranty for complete terms and conditions.

Must be ordered in full case quantity.





LED PAR LAMPS

Ditto™ 7W LED PAR20 lamps

Same PAR20 shape.
Advanced LED technology!

Applications / Features

- Entertainment lighting
- Down lighting
- Display lighting
- Accent lighting
- Dimmable
- 7W PAR20 replaces 50PAR20



Ditto 7W PAR20 LED Lamps



Item Number	Lamp Description	Watts	Volts	CRI	CCT	Lumens	Beam	M.O.L. (Inches)	Life/Hours	Pack
S9080*	7PAR20/LED/25°/3000K/120/D	7	120	80	3000K	415	25°	3 ¼	25,000	24/6
S9081	7PAR20/LED/25°/4000K/120/D	7	120	80	4000K	430	25°	3 ¼	25,000	24/6
S9082*	7PAR20/LED/40°/3000K/120/D	7	120	80	3000K	415	40°	3 ¼	25,000	24/6
S9083	7PAR20/LED/40°/4000K/120/D	7	120	80	4000K	430	40°	3 ¼	25,000	24/6

* ENERGY STAR certified.



Pack: Master 24 / Inner 6/1

Ditto™ 11W LED PAR30 short neck lamps

Same PAR30 shape.
Advanced LED technology!

Applications / Features

- Entertainment lighting
- Down lighting
- Display lighting
- Accent lighting
- Dimmable
- 11W PAR30 replaces up to 75PAR30



Ditto 11W PAR30 LED Short Neck Lamps



Item Number	Lamp Description	Watts	Volts	CRI	CCT	Lumens	Beam	M.O.L. (Inches)	Life/Hours	Pack
S9084	11PAR30/SN/LED/25°/3000K/120/D	11	120	80	3000K	750	25°	3 ⅝	25,000	12/6
S9085	11PAR30/SN/LED/25°/4000K/120/D	11	120	80	4000K	780	25°	3 ⅝	25,000	12/6
S9086	11PAR30/SN/LED/40°/3000K/120/D	11	120	80	3000K	750	40°	3 ⅝	25,000	12/6
S9087	11PAR30/SN/LED/40°/4000K/120/D	11	120	80	4000K	780	40°	3 ⅝	25,000	12/6

Pack: Master 12 / Inner 6/1



LED PAR LAMPS

Ditto™ 11W LED PAR30 long neck lamps

Same PAR30 shape.
Advanced LED technology!

Applications / Features

- Entertainment lighting
- Down lighting
- Display lighting
- Accent lighting
- Dimmable
- 11W PAR30 replaces up to 75PAR30



Ditto 11W PAR30 Long Neck LED Lamps

Item Number	Lamp Description	Watts	Volts	CRI	CCT	Lumens	Beam	M.O.L. (Inches)	Life/Hours	Pack
S9088*	11PAR30/LN/LED/25°/3000K/120/D	11	120	80	3000K	750	25°	4 7/16	25,000	12/6
S9089	11PAR30/LN/LED/25°/4000K/120/D	11	120	80	4000K	780	25°	4 7/16	25,000	12/6
S9090*	11PAR30/LN/LED/40°/3000K/120/D	11	120	80	3000K	750	40°	4 7/16	25,000	12/6
S9091*	11PAR30/LN/LED/40°/4000K/120/D	11	120	80	4000K	780	40°	4 7/16	25,000	12/6

* ENERGY STAR certified.



Pack: Master 12 / Inner 6/1

Ditto™ 17W LED PAR38 lamps

Same PAR38 shape.
Advanced LED technology!

Applications / Features

- Entertainment lighting
- Down lighting
- Display lighting
- Dimmable
- Accent lighting
- 17W PAR38 replaces 90PAR38



Ditto 17W PAR38 LED Lamps

Item Number	Lamp Description	Watts	Volts	CRI	CCT	Lumens	Beam	M.O.L. (Inches)	Life/Hours	Pack
S9092*	17PAR38/LED/25°/3000K/120/D	17	120	80	3000K	1200	25°	5 3/16	25,000	12/6
S9093	17PAR38/LED/25°/4000K/120/D	17	120	80	4000K	1250	25°	5 3/16	25,000	12/6
S9094*	17PAR38/LED/40°/3000K/120/D	17	120	80	3000K	1200	40°	5 3/16	25,000	12/6
S9095	17PAR38/LED/40°/4000K/120/D	17	120	80	4000K	1250	40°	5 3/16	25,000	12/6

* ENERGY STAR certified.



Pack: Master 12 / Inner 6/1

LED PAR & MR16 LED LAMPS

MR16 LED lamps

Applications / Features

- Down lighting
- Accent lighting
- Pendant lighting
- Dimmable



MR16 LED Lamps

Available April 2015



Item Number	Lamp Description	Watts	Volts	CRI	CCT	Lumens	Beam	M.O.L. (Inches)	Life/Hours	Pack
S9008	5MR16/LED/3000K/GU10/D	5	120	80	3000K	370	40°	2 1/8	25,000	12/1
S9009	5MR16/LED/5000K/GU10/D	5	120	80	5000K	400	40°	2 1/8	25,000	12/1
S9098	5MR16/LED/2700K/GU10/D	5	120	80	2700K	560	40°	2 1/8	25,000	12/1
S9096*	7MR16/LED/3000K/GU10/D	7	120	80	3000K	520	40°	2 1/8	25,000	12/1
S9097	7MR16/LED/5000K/GU10/D	7	120	80	5000K	560	40°	2 1/8	25,000	12/1
S9103*†	7MR16/LED/40°/27K/12V/D	7	12	80	2700K	500	40°	1 7/8	25,000	12/1
S9104*†	7MR16/LED/40°/3K/12V/D	7	12	80	3000K	520	40°	1 7/8	25,000	12/1
S9105†	7MR16/LED/40°/4K/12V/D	7	12	80	4000K	540	40°	1 7/8	25,000	12/1
S9106†	7MR16/LED/40°/5K/12V/D	7	12	80	5000K	560	40°	1 7/8	25,000	12/1
S9204*	8MR16/LED/40/2700K/COB	8	12	80	2700K	580	40°	2	25,000	6/1
S9205*	8MR16/LED/40/3500K/COB	8	12	80	3500K	620	40°	2	25,000	6/1
S9206*	8MR16/LED/40/4000K/COB	8	12	80	4000K	630	40°	2	25,000	6/1
S9207*	8MR16/LED/40/5000K/COB	8	12	80	5000K	650	40°	2	25,000	6/1

* ENERGY STAR certified.



All 12V MR16 lamps are compatible with electronic and magnetic transformers

† Approved for totally enclosed fixtures

LED PAR16 lamp

Applications / Features

- Down lighting
- Accent lighting
- Pendant lighting
- Dimmable
- 6PAR16 replaces 45PAR16



LED PAR16 Lamps

Item Number	Lamp Description	Watts	Volts	CRI	CCT	Lumens	Beam	M.O.L. (Inches)	Life/Hours	Pack
S8990	5PAR16/LED/3000K	5	120	80	3000K	370	40°	3 1/4	25,000	12/1

Pack: Master 48/12/1 (Carded)

DECORATIVE LED LAMPS

Decorative LED lamps

Applications / Features

- Accent lighting
- Pendant lighting
- Dimmable




S9200, S9201,
S9202, S9203




S8982



S8981, S8996,
S8983



Beam Angle: 175°



Beam Angle: 240°



Decorative LED Lamps

Item Number	Lamp Description	Watts	Volts	CRI	CCT	Lumens	Beam	M.O.L. (Inches)	Life/Hours	Pack
S8996	3CTC/LED/3000K/E12	3	120	80	3000K	165	240°	3 ¾	25,000	12/1
S8983*	5CTC/LED/2700K/E12	5	120	80	2700K	300	240°	3 ¾	25,000	12/1
S8981*	5CTC/LED/3000K/E12	5	120	80	3000K	310	240°	3 ¾	25,000	12/1
S8982*	5ETC/LED/3000K/E26	5	120	80	3000K	310	240°	3 ¾	25,000	12/1
S9200**	6G25/LED/27K/450L/120/D	6	120	180	2700K	450	175°	4 ¼	25,000	6/1
S9201**	6G25/LED/30K/470L/120/D	6	120	180	3000K	470	175°	4 ¼	25,000	6/1
S9202	6G25/LED/40K/490L/120/D	6	120	180	4000K	490	175°	4 ¼	25,000	6/1
S9203	6G25/LED/50K/510L/120/D	6	120	180	5000K	510	175°	4 ¼	25,000	6/1

* ENERGY STAR certified.



** ENERGY STAR pending - March 2015.

LED DOWNLIGHT RETROFITS

4" to 6" KolourOne Sprint™ 13.5W LED downlight retrofit

Applications / Features

- Indoor residential and commercial lighting
- Replaces incandescent medium base 120V lamps
- Works with 4" to 6" cans
- Dimmable
- Color rings included



KolourOne Sprint™ Downlight Retrofit LED Lamps






Item Number	Lamp Description	Watts	Volts	CRI	CCT	Lumens	Beam	M.O.L. (Inches)	Life/Hours	Pack
S8848	13.5 WLED/DLR-SPRINT	13.5	120	84	2700K	860	110°	6 5/8 - 8	25,000	6/1

Pack: Master 6/1

4" LED recessed downlight retrofit

Applications / Features

- Residential
- Office
- Retail
- Hospitality
- Dimmable
- Damp location listed - Gimbal
- Wet location listed - Baffle



4" LED Recessed Downlight Retrofit

Item Number	Lamp Description	Watts	Volts	Base	CRI	CCT	Lumens	Beam	M.O.L. (Inches)	Life/Hours	Pack
S9195	8WLED/RDL/4/120V/27K/BFL	8	120	E26	80	2700K	560	90°	2 5/8	35,000	12/6
S9116	9WLED/RDL/4/120V/GMBL	9	120	E26*	90	3000K	650	40°	2 1/2	35,000	12/6
S9117	8WLED/RDL/4/120V/BFL	8	120	E26*	90	3000K	500	90°	2 5/8	35,000	12/6

* GU10 base sold separately, item number: S9000


Pack: Master 12 / Inner 6/1

LED DOWNLIGHT RETROFITS



5", 6" LED recessed downlight retrofit

Applications / Features

- Residential
- Office
- Retail
- Hospitality
- Dimmable
- Wet location listed



S9118, S9119, S9196
For use with 5" and 6" recessed fixtures



5", 6" LED Recessed Downlight Retrofit

Item Number	Lamp Description	Watts	Volts	Base	CRI	CCT	Lumens	Beam	M.O.L. (Inches)	Life/Hours	Pack
S9196	11WLED/RDL/5-6/120V/BFL	11	120	E26*	80	2700K	800	90°	3 3/8	35,000	12/1
S9118	11WLED/RDL/5-6/120V/BFL	11	120	E26*	90	3000K	750	90°	3 3/8	35,000	12/1
S9119	15WLED/RDL/5-6/120V/BFL	15	120	E26*	90	3000K	1200	90°	3 3/8	35,000	12/1

* GU24 base sold separately, item number: S8999

Pack: Master 12 / Inner 1

Recessed downlight retrofit kits

Applications / Features

- Residential
- Office
- Retail
- Hospitality
- Dimmable
- Damp location listed - Gimbal
- Wet location listed - Baffle




Remodler kit includes recessed can



Hanger bars & pan (sold separately) for new construction

S9178 Hanger bars & 4" pan



S9179 Hanger bars & 5"-6" pan

Recessed Downlight Retrofit Kits

Item Number	Lamp Description	Watts	Volts	Base	CRI	CCT	Lumens	Beam	M.O.L. (Inches)	Life/Hours	Pack
S9121	10WLED/RDL/4BFL/KIT/120V	10	120	Connector	80	3000K	480	90°	6	35,000	6/1
S9120	10.4WLED/RDL/4GBL/KIT/120V	10.4	120	Connector	80	3000K	437	90°	6	35,000	6/1
S9122	11.6WLED/RDL/5-6BFL/KIT120V	11.6	120	Connector	80	3000K	680	90°	6	35,000	6/1

Pack: Master 6/1



LED RECESSED DOWNLIGHTS

12V Recessed downlight retrofits

Applications / Features


- Residential
- Office
- Retail
- Hospitality
- Dimmable
- Damp location listed - Gimbal
- Wet location listed - Baffle
- Works with magnetic and electronic 12V transformers



S9128
3" Baffle



S9130
4" Baffle



S9129
4" Gimbal



Bi-Pin
Adapter
included

Recessed Downlight Retrofits 12V

Item Number	Lamp Description	Watts	Volts	Base	CRI	CCT	Lumens	Beam	M.O.L. (Inches)	Life/Hours	Pack
S9128	7WLED/RDL/3BFL/12V	7	12	GU5.3	90	3000K	400	90°	3	35,000	12/1
S9129	7WLED/RDL/4GBL/12V	7	12	GU5.3	90	3000K	430	90°	4	35,000	12/1
S9130	8WLED/RDL/4BFL/12V	8	12	GU5.3	90	3000K	460	90°	3 5/8	35,000	12/1

Pack: Master 12/1

120V Recessed downlight retrofits

Applications / Features


- Residential
- Office
- Retail
- Hospitality
- Dimmable
- Damp location listed - Gimbal
- Wet location listed - Baffle



S9126, S9127
5"-6" Baffle



S9125
5"-6" Gimbal



S9123
4" Gimbal



S9124
4" Baffle



E26 Adapter
included

Recessed Downlight Retrofits 120V

Item Number	Lamp Description	Watts	Volts	Base	CRI	CCT	Lumens	Beam	M.O.L. (Inches)	Life/Hours	Pack
S9123	8WLED/RDL/4GBL/120V	8	120	Med.	90	3000K	410	90°	4	35,000	12/1
S9124	8.5WLED/RDL/4BFL/120V	8.5	120	Med.	90	3000K	480	90°	3 5/8	35,000	12/1
S9125	11WLED/RDL/5-6GBL/120V	11	120	Med.	90	3000K	635	90°	4 1/4	35,000	12/1
S9126	13WLED/RDL/5-6BFL/120V	13	120	Med.	90	3000K	820	90°	3 3/4	35,000	12/1
S9127	20WLED/RDL/5-6BFL/120V	20	120	Med.	90	3000K	1210	90°	4	35,000	12/1

Pack: Master 12/1



LED FLUSH FIXTURES & SPECIALTY LAMPS

7" LED flush mount fixture


Applications/ Features

- Kitchens
- Bathrooms
- Hallways
- Offices
- Edge lit LED
- Dimmable*
- Damp location listed
- Includes 3-1/2" mounting screws



Fits 4" junction box

Light Distribution



Fits 4", 3" & Pancake junction boxes

Illuminance at a Distance

Center Beam Lux	Beam V	Lux H
7 Ft 90.65 LUX	18 Ft	18 Ft
13 Ft 22.65 LUX	36 Ft	36 Ft
20 Ft 10.07 LUX	54 Ft	54 Ft
26 Ft 5.67 LUX	72 Ft	72 Ft
33 Ft 3.63 LUX	91 Ft	91 Ft
39 Ft 2.52 LUX	109 Ft	109 Ft

Vert. 5 Spread: 108.2 Vert. 5 Spread: 108.2

7" LED Flush Mount Fixture



Item Number	Lamp Description	Watts	Volts	Finish	CRI	CCT	Lumens	Beam	M.O.L. (Inches)	Life/Hours	Pack
S9190	13.5WLED/7FL/WH/27K	13.5	120	White	180	2700K	810	108°	1	40,000	12/1
S9099	13.5WLED/7FL/WH/3K	13.5	120	White	180	3000K	820	108°	1	40,000	12/1
S9191	13.5WLED/7FL/WH/5K	13.5	120	White	180	5000K	890	108°	1	40,000	12/1
S9192	13.5WLED/7FL/SN/3K	13.5	120	Satin Nickel	180	3000K	820	108°	1	40,000	12/1
S9193	13.5WLED/7FL/WH/3K/1.8	13.5	120	White	180	3000K	820	108°	1.8	40,000	12/1
S9194	13.5WLED/7FL/SN/3K/1.8	13.5	120	Satin Nickel	180	3000K	820	108°	1.8	40,000	12/1

* Consult Satco or visit www.satco.com for an up to date dimmer compatibility list.

Pack: Master 12/1

LED elevator lamps

Applications / Features

- Elevator lighting
- Display lighting
- Non dimmable

Not for use with dimmers. Recommended for use with magnetic transformers. Compatibility with electronic transformers minimum load requirement must be verified.



S9005

S9004

LED Elevator Lamps

Item Number	Lamp Description	Watts	Volts	CRI	CCT	Lumens	Beam	M.O.L. (Inches)	Life/Hours	Pack
S9005	2W/GBF/LED/12V/BA15D	2	12	80	3000K	120	40°	1 3/4	30,000	48/12
S9004	3W/1383/LED/12V/BA15S	3	12	80	3000K	120	40°	2 1/2	30,000	48/12

Indoor use only. Not for use in totally enclosed fixtures.

Pack: Master 48 / Inner 12/1

LED SPECIALTY LAMPS

LED replacements for Halogen G4, G9 and BA15S lamps

Applications / Features

- Solid state LED lighting
- High efficacy
- Long life
- Omni-directional light
- G9 Dimmable and non-dimmable
- G4, BA15S

Available April 2015



LED Replacements for Halogen G4, G9 and BA15S lamps


Item Number	Lamp Description	Watts	Volts	Base	CRI	CCT	Lumens	M.O.L. (Inches)	Life/ Hours	Pack
G4 Bi-Pin										
S9220	LED/2.3W/JC/G4/3000K	2.3	12	G4	80	3000K	180	1 3/4	15,000	50/1
S9221	LED/2.3W/JC/G4/5000K	2.3	12	G4	80	5000K	180	1 3/4	15,000	50/1
BA15S - Landscape										
S9222	LED/2.3W/BA15S/3000K	2.3	12	BA15S	80	3000K	180	2	15,000	50/1
S9223	LED/2.3W/BA15S/5000K	2.3	12	BA15S	80	5000K	180	2	15,000	50/1
G9										
S9224	LED/3.0W/G9/220L/3000K/DIM	3	120	G9	80	3000K	220	2 1/8	15,000	50/1
S9225	LED/3.0W/G9/220L/5000K/DIM	3	120	G9	80	5000K	220	2 1/8	15,000	50/1
S9226	LED/5.0W/G9/450L/3000K	5	120	G9	80	3000K	450	2 1/8	15,000	20/1
S9227	LED/5.0W/G9/450L/5000K	5	120	G9	80	5000K	450	2 1/8	15,000	20/1
S9228	LED/5.0W/G9/360L/3000K/DIM	5	120	G9	80	3000K	350	2 1/8	15,000	20/1
S9229	LED/5.0W/G9/360L/5000K/DIM	5	120	G9	80	5000K	350	2 1/8	15,000	20/1

Pack: Master 50 / Inner 1
Pack: Master 20 / Inner 1

2W miniature LED lamps

Applications / Features

- Landscape lighting
- Display lighting
- Accent lighting
- Security lighting
- Non dimmable



Landscape BA15S
S8968

G4 Bi-Pin
S8969

2W Miniature LED Lamps

Item Number	Lamp Description	Watts	Volts	CRI	CCT	Lumens	Beam	M.O.L. (Inches)	Life/ Hours	Pack
S8968	2W/LANDSCAPE/BA15S	2	12	80	3000K	100	360°	1 5/8	25,000	24
S8969	2W/G4/BI-PIN	2	12	80	3000K	110	360°	1 5/8	25,000	24

Pack: Master 24

LED RETROFIT KIT

Motivation® circular LED module retrofit kit

Featuring KolourOne™ LED technology

LED Retrofit Kit easily converts most standard flushmount fixtures to Energy Efficient, Environmentally Friendly LED Lighting. Kit includes instructions and all hardware necessary for installation into a wide variety of fixtures.

Features:

- Multiple mounting methods for ease of installation. Please read instructions for best mounting method for your fixture type.
- No external driver or heat sink, making module easily replaceable
- Simple plug in power feed (Plug and Play)
- Sleek, space saving design allows for installation into many fixture types (8.125"D x 0.75"H)
- cUL Damp location listed
- cETL Listed as a recognized component for retrofit
- Module is listed by ENERGY STAR® as a certified sub-component
- Available in two color temperatures (2700K & 3500K)
- High lumen output with excellent color rendering. Savings of 80% over comparable incandescent lamps.
- Dimmable with low voltage electronic dimmers
- 30,000 hour rated life
- 3 year warranty

Specifications:

- Construction: Molded body with 5VA rated clear optic polycarbonate lens
- Power supply: 120 VAC
- Light source: Wooree/KolourOne 5050 LED's 2700K & 3000K
- Finish: White body with clear optic lens
- Dimming: Dimming to 15% with low voltage electronic dimmer
- Standards: cUL Listed damp location (E359393) cETL Listed recognized component for retrofit (4009498)
- Certifications: LED Module in certified sub-component data base (CSD) listing by ENERGY STAR®



Each kit contains:

- 1-Circular light engine (shown above)
- 1-Power feed
- 6-Small wire nuts
- 6-Medium wire nuts
- 1-Center mount lock down kit
 - Lock-down retaining ring
 - 1" Check ring
 - Metal washer
 - Rubber washer
- 1-Magnetic lock down kit (3) - 1/2" x 1/8" Magnets
- 1-Self tapping screw lock down kit (3) - 1" Self-Tapping #4 Screws
- Assorted snap-in wire grommets (4 x 2 Each)
- 7/8" #4-40 Machine Screws & Nuts (3 Each)
- Instructions and wiring diagrams

Circular LED Module Retrofit Kit

Item Number	Lamp Description	Watts	Volts	CRI	CCT	Lumens	Beam	M.O.L. (Inches)	Life/Hours	Pack
S9131	19.5W/LED/CIRCLE MODULE/27K	19.5	120	84	2700K	1420	110°	8 1/4 (DIA.)	30,000	10
S9132	19.5W/LED/CIRCLE MODULE/35K	19.5	120	83	3500K	1450	110°	8 1/4 (DIA.)	30,000	10

* Consult Satco or visit www.satco.com for an up to date dimmer compatibility list.

** See separate warranty for complete terms and conditions.

Pack: Master 10

LED SPECIALTY LAMPS

Filament LED lamps

Applications / Features

- LED with a traditional incandescent look and feel
- Omni-directional light source
- Smooth dimming
- Replaces up to 60 Watt lamps
- Long life – 15,000 hours

Available April 2015

Filament LED lamps

Item Number	Lamp Description	Watts	Bulb Type	Base	Volts	Finish	CCT	Lumens	CRI	M.O.L. (Inches)	Life/Hours	Pack
S9251	4.5A19/CL/LED/E26/27K/120V	4.5	A19	E26	120	Clear	2700K	470	80	4 1/8	15,000	24/1
S9252	6.5A19/CL/LED/E26/27K/120V	6.5	A19	E26	120	Clear	2700K	810	80	4 1/8	15,000	24/1
S9254	4.5G25/CL/LED/E26/27K/120V	4.5	G25	E26	120	Clear	2700K	470	80	4 3/8	15,000	24/1
S9255	6.5G25/CL/LED/E26/27K/120V	6.5	G25	E26	120	Clear	2700K	810	80	4 3/8	15,000	24/1
S9256	4.5G40/CL/LED/E26/27K/120V	4.5	G40	E26	120	Clear	2700K	470	80	6 3/8	15,000	24/1
S9257	6.5G40/CL/LED/E26/27K/120V	6.5	G40	E26	120	Clear	2700K	810	80	6 3/8	15,000	24/1
S9260	4.5ETC/LED/27K/120V	4.5	C35	E26	120	Clear	2700K	470	80	3 1/2	15,000	24/1
S9261	4.5CTC/LED/27K/120V	4.5	C35	E12	120	Clear	2700K	470	80	4 5/16	15,000	24/1
S9264	4.5EFC/LED/27K/120V	4.5	CA35	E26	120	Clear	2700K	470	80	4 5/16	15,000	24/1
S9265	4.5CFC/LED/27K/120V	4.5	CA35	E12	120	Clear	2700K	470	80	5	15,000	24/1
S9268	4.5BT15/CL/LED/E26/27K/120V	4.5	BT15	E26	120	Clear	2700K	470	80	4 1/8	15,000	24/1
S9269	6.5BT15/CL/LED/E26/27K/120V	6.5	BT15	E26	120	Clear	2700K	810	80	4 1/8	15,000	24/1
S9270	2.5ST19/AMB/LED/E26/23K/120V	2.5	ST19	E26	120	Amber	2300K	220	80	2 3/8	15,000	24/1
S9271	4.5ST19/AMB/LED/E26/23K/120V	4.5	ST19	E26	120	Amber	2300K	470	80	5 3/8	15,000	24/1
S9272	6.5ST19/AMB/LED/E26/23K/120V	6.5	ST19	E26	120	Amber	2300K	810	80	5 3/8	15,000	24/1
S9273	4.5A15/CL/LED/E26/237K/120V	4.5	A15	E26	120	Clear	2700K	810	80	4 1/8	15,000	24/1



S9252



S9264



S9260



S9269



S9265



S9261



S9272

LED SPECIALTY LAMPS

Carded specialty LED lamps

Applications / Features

- Sign bulbs
- Indicator
- Nightlights
- Decorative lamps
- Non-dimmable
- Direct replacements for incandescent & specialty lamps
- LED replacements use 80% less energy
- Long life; 25,000
- Wet location

28 new LED products for use in multiple residential and commercial applications. Merchandising plan-o-grams available.



Carded Specialty LED Lamps

Item Number	Lamp Description	Watts	Base	Volts	Finish	CCT	Lumens	M.O.L. (Inches)	Life/Hours	Pack
S9150	1.4W A15/CL/LED/120V/CD	1.4	Med.	120	Clear	2700K	36	3 15/16	25,000	12/1
S9151	1.4W A15/FR/LED/120V/CD	1.4	Med.	120	Frost	2700K	45	3 15/16	25,000	12/1
S9152	1W CTC/LED/120V/CD	1.0	Cand.	120	Clear	2700K	25	3 9/16	25,000	12/1
S9153	1W CFC/LED/120V/CD	1.0	Cand.	120	Clear	2700K	25	3 7/8	25,000	12/1
S9154	1.4W ETC/LED/120V/CD	1.4	Med.	120	Clear	2700K	36	3 13/16	25,000	12/1
S9155	1W CTD/LED/CRYSTAL/120V/CD	1.0	Cand.	120	Clear	2700K	25	3 9/16	25,000	12/1
S9156	0.5W C7/CL/LED/120V/CD	0.5	Cand.	120	Clear	2700K	14	2 1/16	25,000	12/1
S9157	0.5W C7/WH/LED/120V/CD	0.5	Cand.	120	White	2700K	14	2 1/16	25,000	12/1
S9158	1.4W G16.5/CL/LED/120V/CD	1.4	Med.	120	Clear	2700K	36	2 3/4	25,000	12/1
S9159	1.4W G16.5/WH/LED/120V/CD	1.4	Med.	120	White	2700K	45	2 13/16	25,000	12/1
S9160	1.2W S11/CL/LED/120V/CD	1.2	Med.	120	Clear	2700K	32	2 5/16	25,000	12/1
S9161	1.2W S11/WH/LED/120V/CD	1.2	Med.	120	White	2700K	40	2 5/16	25,000	12/1
S9162	1.2W S11/BL/LED/120V/CD	1.2	Med.	120	Blue	—	—	2 5/16	25,000	12/1
S9163	1.2W S11/GR/LED/120V/CD	1.2	Med.	120	Green	—	—	2 5/16	25,000	12/1
S9164	1.2W S11/OR/LED/120V/CD	1.2	Med.	120	Orange	—	—	2 5/16	25,000	12/1
S9165	1.2W S11/RED/LED/120V/CD	1.2	Med.	120	Red	—	—	2 5/16	25,000	12/1
S9166	1.2W S11/Y/LED/120V/CD	1.2	Med.	120	Yellow	—	—	2 5/16	25,000	12/1
S9167	1.0W S11/CL/LED/E17/120V/CD	1.0	Inter.	120	Clear	2700K	28	2 5/16	25,000	12/1
S9168	1.0W S11/WH/LED/E17/120V/CD	1.0	Inter.	120	White	2700K	35	2 5/16	25,000	12/1
S9169	1.4W S14/Y/LED/120V/CD	1.4	Med.	120	Yellow	—	—	3 5/16	25,000	12/1
S9170	1.4W S14/RED/LED/120V/CD	1.4	Med.	120	Red	—	—	3 5/16	25,000	12/1
S9171	1.4W S14/GR/LED/120V/CD	1.4	Med.	120	Green	—	—	3 5/16	25,000	12/1
S9172	1.4W S14/BL/LED/120V/CD	1.4	Med.	120	Blue	—	—	3 5/16	25,000	12/1
S9173	1.4W S14/OR/LED/120V/CD	1.4	Med.	120	Orange	—	—	3 5/16	25,000	12/1
S9174	1.4W S14/CL/LED/120V/CD	1.4	Med.	120	Clear	2700K	36	3 5/16	25,000	12/1
S9175	1.4W S14/FR/LED/120V/CD	1.4	Med.	120	Frost	2700K	45	3 5/16	25,000	12/1
S9176	0.8W T6/FR/LED/120V/CD	0.8	Cand.	120	Frost	2700K	25	2 1/16	25,000	12/1
S9177	0.8W T6/CL/LED/120V/CD	0.8	Cand.	120	Clear	2700K	20	2 1/16	25,000	12/1

Pack: Master 48 / Inner 12/1

LED T8 LAMPS

Direct replacement for linear fluorescent T8 lamps in existing fixtures with instant or rapid start ballasts. No rewiring required*.

KolourOne LED T8 lamps

Applications/ Features

- Over 40% energy savings vs standard 4' T8 systems
- All glass tube - eliminating the possibility of yellowing
- Direct replacement solution allows the fixture to maintain the Original UL and CSA Compliance
- Long life - 50,000 hours
- Instant on to full brightness / no flicker
- DLC listed
- 5 Year warranty



KolourOne LED T8 Lamps

Item Number	Lamp Description	Watts	Volts	CRI	Base Type	CCT	Lumens	M.O.L. (Inches)	Life/Hours	Pack
S9230	17.5T8/LED/48-3000K/DLC	17.5	120-277	80+	Med Bi-Pin	3000K	2080	48	50,000	10
S9231	17.5T8/LED/48-3500K/DLC	17.5	120-277	80+	Med Bi-Pin	3500K	2160	48	50,000	10
S9232	17.5T8/LED/48-4000K/DLC	17.5	120-277	80+	Med Bi-Pin	4000K	2200	48	50,000	10
S9233	17.5T8/LED/48-5000K/DLC	17.5	120-277	80+	Med Bi-Pin	5000K	2230	48	50,000	10

* May not be compatible with all rapid start ballasts. Contact Satco (800-437-2826) for an approved list.

Pack: Master 10

Satco LED T8 lamps

Applications/ Features

- Over 40% energy savings vs standard 4' T8 systems
- All glass tube - eliminating the possibility of yellowing
- Direct replacement solution allows the fixture to maintain the Original UL and CSA Compliance
- Long life- 50,000 hours
- Instant on to full brightness / no flicker
- DLC listed
- 5 year warranty



Available April 2015



LED Fluorescent Replacement Lamps

Item Number	Lamp Description	Watts	Volts	CRI	Base Type	CCT	Lumens	M.O.L. (Inches)	Life/Hours	Pack
S9234	14T8/LED/48-830/DR	14	120-277	82	Med Bi-Pin	3000K	1800	48	50,000	10
S9235	14T8/LED/48-835/DR	14	120-277	82	Med Bi-Pin	3500K	1800	48	50,000	10
S9236	14T8/LED/48-840/DR	14	120-277	82	Med Bi-Pin	4000K	1800	48	50,000	10
S9237	14T8/LED/48-850/DR	14	120-277	82	Med Bi-Pin	5000K	1800	48	50,000	10

* May not be compatible with all rapid start ballasts. Contact Satco (800-437-2826) for an approved list.

Pack: Master 10


LED/CFL REPLACEMENT LAMPS

LED/CFL replacement lamps

Direct replacement for 4-pin CFL's with electronic ballasts

Applications/ Features

- Replaces 18, 26, 32, and 42 watt CFLs*
- No re-wiring needed
- Instant on to full brightness / no flickering
- Vertical and horizontal options
- Up to 70% energy saving
- Long life - 50,000 hours
- 3 year warranty
- Dimmable**



LED/CFL Replacement Lamps

Item Number	Lamp Description	Watts	Volts	Base Type	CCT	CRI	M.O.L. (Inches)	Lumens	Life/ Hours	Pack
S9300	13W/V/LED/CFL/827/4P	13	120-277	G24Q	2700K	80	3 5/8	900	50,000	50/10
S9301	13W/V/LED/CFL/835/4P	13	120-277	G24Q	3500K	80	3 5/8	900	50,000	50/10
S9302	13W/V/LED/CFL/840/4P	13	120-277	G24Q	4000K	80	3 5/8	925	50,000	50/10
S9303	13W/V/LED/CFL/850/4P	13	120-277	G24Q	5000K	80	3 5/8	950	50,000	50/10
S9304	13W/VL/LED/CFL/827/4P (Long)	13	120-277	G24Q	2700K	80	4 5/8	900	50,000	50/10
S9305	13W/VL/LED/CFL/835/4P (Long)	13	120-277	G24Q	3500K	80	4 5/8	900	50,000	50/10
S9306	13W/VL/LED/CFL/840/4P (Long)	13	120-277	G24Q	4000K	80	4 5/8	925	50,000	50/10
S9307	13W/VL/LED/CFL/850/4P (Long)	13	120-277	G24Q	5000K	80	4 5/8	950	50,000	50/10
S9308	13W/H/LED/CFL/827/4P	13	120-277	G24Q	2700K	80	5 1/4	900	50,000	50/10
S9309	13W/H/LED/CFL/835/4P	13	120-277	G24Q	3500K	80	5 1/4	900	50,000	50/10
S9310	13W/H/LED/CFL/840/4P	13	120-277	G24Q	4000K	80	5 1/4	925	50,000	50/10
S9311	13W/H/LED/CFL/850/4P	13	120-277	G24Q	5000K	80	5 1/4	950	50,000	50/10

* Fits G24q-2,3,4 sockets

** With compatible dimming ballasts

Pack: Master 50/10

PAR & REFLECTOR LAMP GUIDE



Panel Array 2.0 LED PAR lamps

Satco's Panel Array 2.0 LED lamps deliver smooth general lighting with no harsh cut off and exact color consistency from lamp to lamp due to KolourOne™ optical technologies. These highly engineered lamps are built to take on the toughest indoor commercial & residential applications.

- Smooth optical beam
- 2700K, 3500K and 5000K
- 40° and 60° beam angles
- Dimmable
- Commercial warranty*
- ENERGY STAR certified



Duo indoor/outdoor LED PAR lamps

Duo lamps are engineered by KolourOne™ to excel in tough environments, indoors or out. Exact color matching from lamp to lamp makes them perfect for large indoor or outdoor applications. And the high lumen output and long throw distance makes lighting from high ceilings and creating dramatic outdoor effects no problem.

- Defined optical beam
- Greater throw distance
- 3500K
- 40° Beam angle
- Dimmable
- Commercial warranty*
- Outdoor Use / IP65 rated
- ENERGY STAR certified



Ditto LED PAR lamps

Designed to deliver indoor display and general lighting at a great value. They share the same dimensions as standard PAR lamps making them an easy choice for so many residential or light commercial applications.

- Defined optical beam
- Greater throw distance
- 3000K and 4000K
- 25° and 40° Beam angles
- Dimmable
- Residential warranty**
- ENERGY STAR certified



Ditto LED reflector lamps

The original "consumer friendly" LED replacement-clean/ simple/ familiar. Wide beam angles in many color temperatures make them the first choice for many residential general lighting applications.

- Smooth optical beam
- 2700K, 3000K, 4000K and 5000K
- 105°, 106° and 108° beam angles
- Dimmable
- Residential warranty**
- ENERGY STAR certified

* Commercial or residential use, no limitation on hours per day.

** Residential use based on 4 hours per day.

A19 LAMP GUIDE



Omni-directional 10.5W & 11W A19 LED lamps

Satco omni-directional A19 LED lamps deliver the same light distribution as typical A19 lamps with no shadows and even light. Innovative engineering enables these lamps to deliver a full 360 degrees of illumination and stand up to virtually any commercial applications.

- Full 360° illumination
- 2700K, 3500K and 5000K, E26 base
- GU24 base available in 2700K
- Dimmable
- Commercial warranty*
- ENERGY STAR certified



Multi-directional dimmable 7W & 10W A19 LED lamps

These versatile multi-directional A19 LED's are the perfect choice for many residential applications—lamps, wall fixtures, pendants—with its base choice and wide dimming range. They feature a 3 year warranty and long, 25,000 hour life span.

- 215° illumination
- 2700K and 5000K, E26 base
- GU24 base available in 2700K
- Dimmable
- Direct replacement for 40W & 60W incandescent and 9W & 13W CFL's
- Damp location
- Residential warranty**



Multi-directional non-dimmable 6.4W & 9.8W A19LED lamps

Satco's 6.4W and 9.8W multi-directional A19 LED's are the perfect energy efficient replacement for the 40W & 60W incandescent bulbs. They will lend themselves to a host of household applications while saving energy and lasting at least 25,000 hours.

- 240° illumination
- 2700K and 5000K
- E26 base
- Direct replacement for 40W & 60W incandescent and 9W & 13W screw-in CFL's
- Damp location
- Residential warranty**

**SATCO LED SOLUTIONS.
LED REPLACEMENT LAMPS
THAT ONLY EXPERIENCE
CAN DELIVER.**



