



2016

# Contents

The Great Outdoors®  
by Minka-Lavery® is your home's  
'welcome statement'. Graceful,  
fashionable lighting is the best value  
that you can add to your home.

At The Minka Group®,  
we provide lighting that is decorative  
and in keeping with today's trends.  
Our fixtures meet stringent quality  
and durability guidelines to assure  
you of products that are safe, long  
lasting investments, giving years of  
beauty and security. We ascribe to  
Title 24 and Dark-Sky standards for  
our various collections, recognizing  
we are all an important part of our  
environment and global community.

Please enjoy our 2016 collection on  
the following pages.



Scan to view our online catalog

The products depicted in this catalog are protected by United States Federal and/or State Law, including Patent, Trademark and/or Copyright laws.  
Catalog design and elements of catalog design is protected by United States Federal and/or State Law, including Patent, Trademark and/or Copyright laws.

## LED

Intro	10
• Baytree Lane	12-11
Bay View™	37
Crest Ridge	14-15
Eastborne	33
• Everton	35
• Everton Rain	35
Garreston Pointe	39
Hanford Pointe	18-19
Hillsdale	30-31
Holbrook	36
Kirkham™	13
Lauriston Manor	24-25
Lynhaven	34
Merrimack™	16-17
Mossoro™	26-27
Seneca Square	32
Skyline	38
Talera	20-21
Wickford Bay™	28-29
Wynterfield	22-23

## Incandescent

Intro	40
Abbey Lane™	134-135
Addison Park	130
Amherst™	76-77
Ardmore	64-68
• Astrapia II	96-97
Bay Hill™	141
Bay View™	122-123
Berkeley™	113
• Bexley Manor	41-43
Bridgeport™	138
Casona Square	129
Copperton	50-51
Cranston™	139
Crossroads Point	100-101
Delshire Point	124
Downtown Edison	116
Eastbury	52-53
Edenshire	47-49
Geox	128
Hancock™	84
Harrison™	58-63
Harveston Manor	136-137
• Hawks Point	92-93
Irvington Manor	86-87
Kent Place™	82-83
Ladera	132-133
Lynnfield	120-121
Mallorca™	105-111
Merrimack™	78-79
Morgan Park™	74-75
Mossoro™	88-89
Newport™	69-73
Oxford Road	104
Rivendale Court	94-95
• Rue Vieille	44-46

• Satomi	98-99
Segovia™	140
Settlers Way	118-119
Spyglass Cove	117
Stratford Hall™	54-57
• Sunnybrook	90-91
Taylor Court™	80-81
Townsend™	112
Travessa	131
Vista Delmar	125
Vista Montaire	85
Westgate	126-127
Willow Pointe	114-115
Wilshire Park	102-103
Wyndmere™	117

## Dark-Sky

Intro	142
Artisan Lane	149
Bay Crest™	145
Ceramic	147
Everton	147
Kirkham™	144
Sage Ridge™	143
Soare	148
Vanira Place™	146

## CFL

Intro	150
Abbey Lane™	170-171
Andrita Court™	156-157
Ardmore™	160-161
Aspen™ II	173
Bay View™	176-177
Chelesa Road	168-169
Colva	125
Cranston™	180
Danbury™	180
Delancy™	151-153
Harrison™	164-165
Kent Place™	162-163
Lander Heights™	158-159
Lugarno Square	154
Mallorca™	166-167
Merrimack™	172
Nanti	178
Scottsdale™ II	155
Segovia™	179
Skyline	175
Sterling Heights	174

## Misc

Family Overview	1-9
Basic CFL	181
Flush Mounts	182
Post and Mounts	184
Finishes	185-187
Bulb Chart	189
Measurement Specifications	188
Acknowledgements/Disclaimers	200

# Family Overview

---



Rue Vieille  
Incandescent Page 44-46



Bexley Manor  
Incandescent Page 41-43



Stratford Hall™  
Incandescent Page 54-57



Rivendale Court  
Incandescent Page 94-95



Astrapia II  
Incandescent Page 96-97



Vanira Place™  
Dark-Sky Page 146



Edenshire  
Incandescent Page 47-49



Taylor Court™  
Incandescent Page 80-81



Wickford Bay™  
LED Page 28-29

# Family Overview

---



Hawks Point  
Incandescent Page 92-93



Sunnybrook  
Incandescent Page 90-91



Crossroads Point  
Incandescent Page 100-101



Oxford Road  
Incandescent Page 104



Satomi  
Incandescent Page 98-99



Talera  
LED Page 20-21



Lauriston Manor  
LED Page 24-25



Irvington Manor  
Incandescent Page 86-87



Wilshire Park  
Incandescent Page 102-103

# Family Overview



Morgan Park™  
Incandescent Page 74-75



Ardmore™  
Incandescent Page 64-68  
Compact Fluorescent Page 160-161



Newport  
Incandescent Page 69-73



Hanford Pointe  
LED Page 18-19



Merrimack™  
Incandescent Page 78-79  
LED Page 16-17  
Compact Fluorescent Page 172



Harrison™  
Incandescent Page 58-63  
Compact Fluorescent Page 164-165



Wynterfield  
LED Page 22-23



Amherst™  
Incandescent Page 76-77



Kent Place™  
Incandescent Page 82-83  
Compact Fluorescent Page 162-163

# Family Overview

---



Hancock™  
Incandescent Page 84



Segovia™  
Incandescent Page 140  
Compact Fluorescent Page 179



Bay Hill  
Incandescent Page 141



Ladera  
Incandescent Page 132-133



Travessa  
Incandescent Page 131



Cranston™  
Incandescent Page 139  
Compact Fluorescent Page 180



Andrita Court™  
Compact Fluorescent Page 156-157



Hillsdale  
LED Page 30-31



Mossoro™  
Incandescent Page 88-89  
LED Page 26-27

# Family Overview



Crest Ridge  
LED Page 14-15



Downtown Edison  
Incandescent Page 116



Kirkham™  
LED Page 13  
Dark-Sky Page 144



Danbury™  
Compact Fluorescent Page 180



Baytree Lane  
LED Page 11-12



Bay Crest™  
Dark-Sky Page 145




Wyndmere™  
Incandescent Page 117



Ceramic  
Dark-Sky Page 147



Delshire Point  
Incandescent Page 124



Bay View™  
Incandescent Page 122-123  
LED Page 37  
Compact Fluorescent Page 176-177



Vista Delmar  
Incandescent Page 125

# Family Overview



Harveston Manor  
Incandescent Page 136-137



Chelesa Road™  
Compact Fluorescent Page 168-169



Mallorca™  
Incandescent Page 105-111  
Compact Fluorescent Page 166-167



Lynnfield  
Incandescent Page 120-121



Spyglass Cove  
Incandescent Page 117



Garreston Ridge  
LED Page 39



Settlers Way  
Incandescent Page 118-119



Abbey Lane™  
Incandescent Page 134-135  
Compact Fluorescent Page 170-171



Seneca Square  
LED Page 32



# Family Overview



Scottsdale™ II  
Compact Fluorescent Page 155



Bridgeport™  
Incandescent Page 138



Berkeley™  
Incandescent Page 113



Delancy™  
Compact Fluorescent Page 151-153



Willow Pointe  
Incandescent Page 114-115



Townsend™  
Incandescent Page 112



Eastbury  
Incandescent Page 52-53



Copperton  
Incandescent Page 50-51



Vista Montaire  
Incandescent Page 85

# Family Overview

---



Lynhaven  
LED Page 34



Skyline  
LED Page 38  
Compact Fluorescent Page 175



Geox  
Incandescent Page 128



Everton Rain  
LED Page 35



Westgate  
Incandescent Page 126-127



Everton  
LED Page 35  
Dark-Sky Page 147



Soare  
Dark Sky Page 148



Casona Square  
Incandescent Page 129



Eastborne  
LED Page 33



Colva  
Compact Fluorescent Page 125

# Family Overview



Lugarno Square™  
Compact Fluorescent Page 154



Addison Park  
Incandescent Page 130



Sterling Heights  
Compact Fluorescent Page 174



Artisan Lane  
Dark-Sky Page 149



Holbrook  
LED Page 36



Sage Ridge™  
Dark-Sky Page 143



Lander Heights™  
Compact Fluorescent Page 158-159



Aspen™ II  
Compact Fluorescent Page 173



Nanti  
Compact Fluorescent Page 178

# LED



*With over 32 years of providing the best products at the most cost effective price, Minka® is excited to be an industry leader in energy efficient outdoor lighting. Our vast resources for manufacturing, quality control and logistics have enabled us to develop one of the industry's largest selection of outdoor LED products.*

*The Great Outdoors® proudly introduces eight new families to our existing LED collection for beautiful illumination with an environmental advantage. With uncompromising style, our LED fixtures supply a 3000% energy savings over comparable incandescent lighting. With a life span of 25,000 hours, LEDs are a luminous alternative to standard lighting.*

*Let The Great Outdoors® illuminate your outdoor living spaces with a wide selection of LED outdoor options.*

# Baytree Lane LED

DARK-SKY

LED



LED

71169-A144-L



71163-A144-L

LED

DARK-SKY

**NEW**

Finish:  
Brushed Aluminum

Glass:  
N/A

Features:

- » Aluminum Construction
- » IDA-Approved™
- » 14W, 2,700K LED Incl., CRI 76
- » 3 Year Limited Warranty
- » See Finish Disclaimer on page 200

Item No.	Type	Size	Watt	Lumens
71163-A144-L	Wall Mount	8.5"W x 8.5"H x 11.5" Ext.	14W LED (Incl.)	296
71169-A144-L	Wall Mount	11"W x 9.75"H x 12.75" Ext.	14W LED (Incl.)	335

# Baytree Lane LED



DARK-SKY

LED



71169-143C-L

DARK-SKY

LED

71163-143C-L

LED



DARK-SKY

**NEW**

Finish:  
Oil Rubbed Bronze with Gold Highlights

Glass:  
N/A

- Features:
- » Aluminum Construction
  - » IDA-Approved™
  - » 14W, 2,700K LED Incl., CRI 76
  - » Hand Applied Multi-Step Finish
  - » 3 Year Limited Warranty
  - » See Finish Disclaimer on page 200

Item No.	Type	Size	Watt	Lumens
71163-143C-L	Wall Mount	8.5"W x 8.5"H x 11.5" Ext.	14W LED (Incl.)	296
71169-143C-L	Wall Mount	11"W x 9.75"H x 12.75" Ext.	14W LED (Incl.)	335

DARK-SKY

Kirkham™ LED



8101-A138-L

LED

LED



8102-A138-L



8106-A138-L

LED

DARK-SKY

Finish:  
Aspen Bronze™

Glass:  
Metal Shade

Features:

- » Aluminum Construction
- » Recessed Light Source
- » IDA-Approved™
- » 10W, 2700K LED (Incl.), CRI 80
- » Also available:  
Aspen Bronze™ - Incandescent Dark-Sky,  
page 144
- » 3 Year Limited Warranty
- » See Finish Disclaimer on page 200

Item No.	Type	Size	Watt	Lumens
8101-A138-L	Wall Mount	8.5"W x 6"H x 10.5" Ext.	10W LED (Incl.)	289
8102-A138-L	Wall Mount	11"W x 6.5"H x 12.25" Ext.	10W LED (Incl.)	270
8106-A138-L	Post Mount	11.75"L x 8.5"W x 11"H	10W LED (Incl.)	314

# Crest Ridge **LED**



Canopy Detail

**LED**

**LED**



8134-173-L



8131-173-L

**LED**



8136-173-L



# Crest Ridge LED



LED



LED

8132-173-L

Finish:  
Forged Silver

Glass:  
Etched Opal Glass

- Features:
- » Aluminum Construction
  - » 14W, 2,700K LED (Incl.), CRI 80
  - » Hand Applied Multi-Step Finish
  - » Rod Hung Style can also be used for interior foyer or stairwell applications
  - » 3 Year Limited Warranty
  - » See Finish Disclaimer on page 200

Item No.	Type	Size	Watt	Lumens
8131-173-L	Wall Mount	8"W x 10"H x 8.75" Ext.	14W LED (Incl.)	601
8132-173-L	Wall Mount	10"W x 12.75"H x 10.75" Ext.	14W LED (Incl.)	434
8134-173-L	Rod Hung	10" Dia. x 8.75"H Adjustable to 56"H Max.	14W LED (Incl.)	408
8136-173-L	Post Mount	10" Dia. x 17"H	14W LED (Incl.)	458

# Merrimack™ LED



LED



LED

8763-66-L

Finish:  
Black

Glass:  
Clear Hammered Glass

Features:

- » Cast Aluminum Construction
- » Recessed Light Source
- » 10W, 2700K LED (Incl.), CRI 80
- » Chain Hung Style can also be used for interior foyer or stairwell applications
- » Also available:
  - Corona Bronze™ - Incandescent, page 78
  - Corona Bronze™ - Fluorescent, page 172
- » 3 Year Limited Warranty
- » See Finish Disclaimer on page 200

LED

Item No.	Type	Size	Watt	Lumens
8761-66-L	Wall Mount	6.25"W x 12.25"H x 7.75" Ext.	1-10W LED (Incl.)	234
8762-66-L	Wall Mount	8"W x 16.25"H x 9.5" Ext.	1-10W LED (Incl.)	193
8763-66-L	Wall Mount	10"W x 20"H x 12" Ext.	1-10W LED (Incl.)	221
8764-66-L	Chain Hung	10" Dia. x 18.25"H	1-10W LED (Incl.)	227
8766-66-L	Post Mount	8" Dia. x 19.25"H	1-10W LED (Incl.)	190



LED



8762-66-L

LED



8764-66-L

LED



8766-66-L

LED



8761-66-L

# Hanford Pointe LED



LED



LED

71822-143-L

LED

Finish:  
Oil Rubbed Bronze

Glass:  
Clear Water Glass

- Features:
- » Ever-Pro™ Polymer Construction
  - » 11W and 14W, 2,700K LED (Incl.), CRI 80
  - » Recessed Light Source
  - » Chain Hung Style can also be used for interior foyer or stairwell applications
  - » 3 Year Limited Warranty
  - » See Finish Disclaimer on page 200

Item No.	Type	Size	Watt	Lumens
71821-143-L	Wall Mount	7.75"W x 19"H x 9" Ext.	11W LED (Incl.)	477
71822-143-L	Wall Mount	9"W x 21.75"H x 11.25" Ext.	14W LED (Incl.)	521
71824-143-L	Chain Hung	9"L x 7.75"W x 18.75"H	14W LED (Incl.)	600
71826-143-L	Post Mount	9"L x 7.75"W x 20.25"H	14W LED (Incl.)	626

# Hanford Pointe LED



LED



71824-143-L



71821-143-L

LED



71826-143-L

LED



# Talera LED



LED



73101-143C-L



73102-143C-L

LED



73106-143C-L

LED



LED



73103-143C-L

LED

Finish:  
Oil Rubbed Bronze with Gold Highlights

Glass:  
Clear Water Glass

- Features:
- » Aluminum Construction
  - » Hand Applied Multi-Step Finish
  - » 11W, 2,700K LED (Incl.), CRI 80
  - » 3 Year Limited Warranty
  - » See Finish Disclaimer on page 200

Item No.	Type	Size	Watt	Lumens
73101-143C-L	Wall Mount	5.5"W x 10.75"H x 5.5" Ext.	11W LED (Incl.)	339
73102-143C-L	Wall Mount	7"W x 12.75"H x 7" Ext.	11W LED (Incl.)	385
73103-143C-L	Wall Mount	9"W x 15.75"H x 8.25" Ext.	11W LED (Incl.)	397
73106-143C-L	Post Mount	7"L x 6"W x 15"H	11W LED (Incl.)	358

# Wynterfield LED



LED



LED

72413-51A-L

Finish:  
Burnt Rust

Glass:  
Clear Seeded Glass

Features:

- » Aluminum Construction
- » Recessed Light Source
- » 10W, 2700K LED (Incl.), CRI 80
- » Chain Hung Style can also be used for interior foyer or stairwell applications
- » 3 Year Limited Warranty
- » See Finish Disclaimer on page 200

Item No.	Type	Size	Watt	Lumens	Notes
72411-51A-L	Wall Mount	6.75"W x 15.5"H x 8.25" Ext.	10W LED (Incl.)	164	
72412-51A-L	Wall Mount	8.5"W x 19"H x 9.75" Ext.	10W LED (Incl.)	177	
72413-51A-L	Wall Mount	10"W x 22.25"H x 11.75" Ext.	10W LED (Incl.)	182	
72414-51A-L	Chain Hung	8.5" Dia. x 19"H	10W LED (Incl.)	209	
72416-51A-L	Post Mount	8.5" Dia. x 19.25"H	10W LED (Incl.)	166	Clear Seeded Glass and Frosted White Glass



# Wynterfield LED



LED

72414-51A-L



72412-51A-L



72411-51A-L

LED



LED

72416-51A-L

# Lauriston Manor LED



72391-143C



72392-143C

LED

LED



72396-143C



72393-143C

LED

# Lauriston Manor LED



LED



LED

72397-143C

LED

Finish:  
Oil Rubbed Bronze with Gold Highlights

Glass:  
Clear Seeded Glass

- Features:
- » Aluminum Construction
  - » Hand Applied Multi-Step Finish
  - » Recessed Light Source
  - » 10W, 2,700K LED (Incl.), CRI 80
  - » 3 Year Limited Warranty
  - » See Finish Disclaimer on page 200

Item No.	Type	Size	Watt	Lumens
72391-143C	Wall Mount	5.5"W x 10"H x 7" Ext.	10W LED (Incl.)	242
72392-143C	Wall Mount	7"W x 13"H x 8.75" Ext.	10W LED (Incl.)	210
72393-143C	Wall Mount	9"W x 15.75"H x 11" Ext.	10W LED (Incl.)	216
72396-143C	Post Mount	7"L x 7"W x 15"H	10W LED (Incl.)	211
72397-143C	Wall Mount	11"W x 19.25"H x 13.25" Ext	10W LED (Incl.)	271

# Mossoro™ LED



8267-66-L

Finish:  
Black

Glass:  
Clear Seeded Glass

LED

**Features:**

- » Aluminum Construction
- » Recessed Light Source
- » 11W, 2,700K LED (Incl.), CRI 80
- » Chain Hung Style can also be used for interior foyer or stairwell applications
- » Also available:  
Mossoro Walnut™ - Incandescent, page 89
- » 3 Year Limited Warranty
- » See Finish Disclaimer on page 200



8261-66-L

LED



8263-66-L

Item No.	Type	Size	Watt	Lumens
8261-66-L	Wall Mount	5.75"W x 14.25"H x 7" Ext.	11W LED (Incl.)	400
8262-66-L	Wall Mount	7.75"W x 17.75"H x 9" Ext.	11W LED (Incl.)	387
8263-66-L	Wall Mount	9.75"W x 22.75"H x 11.25" Ext.	11W LED (Incl.)	395
8264-66-L	Chain Hung	9.75"L x 9.75"W x 19"H	11W LED (Incl.)	439
8265-66-L	Post Mount	11.5"L x 11.5"W x 23.5"H	11W LED (Incl.)	282
8266-66-L	Post Mount	7.75"L x 7.75"W x 16.75"H	11W LED (Incl.)	294
8267-66-L	Wall Mount	11.5"W x 26.75"H x 13.25" Ext.	11W LED (Incl.)	373



8264-66-L

LED



8262-66-L

LED

LED



8265-66-L

LED



8266-66-L

# Wickford Bay™ LED



LED



LED

Finish:  
Iron Oxide

Glass:  
Clear Seeded Glass

- Features:
- » Aluminum Construction
  - » Recessed Light Source
  - » 10W, 2700K LED (Incl.), CRI 80
  - » Chain Hung Style can also be used for interior foyer or stairwell applications
  - » 3 Year Limited Warranty
  - » See Finish Disclaimer on page 200

8273-A357-L

LED

Item No.	Type	Size	Watt	Lumens
8271-A357-L	Wall Mount	6.75"W x 10.25"H x 7.25" Ext.	10W LED (Incl.)	177
8272-A357-L	Wall Mount	9"W x 19.5"H x 9.25" Ext.	10W LED (Incl.)	231
8273-A357-L	Wall Mount	11.25"W x 22"H x 12" Ext.	10W LED (Incl.)	218
8274-A357-L	Chain Hung	11.25"L x 11.25"W x 14.25"H	10W LED (Incl.)	235
8276-A357-L	Post Mount	11.25"L x 11.25"W x 18"H	10W LED (Incl.)	197

# Wickford Bay™ LED



8274-A357-L

LED



8272-A357-L

LED



8276-A357-L

8271-A357-L



LED

# Hillsdale LED



LED



8164-615B-L



8161-615B-L

LED

LED



8166-615B-L





LED



8162-615B-L

LED

LED

Finish:  
Dorian Bronze™

Glass:  
Clear Seeded Glass

- Features:
- » Aluminum Construction
  - » 14W, 2,700K LED (Incl.), CRI 80
  - » Recessed Light Source
  - » Hand Applied Multi-Step Finish
  - » Chain Hung Style can also be used for interior foyer or stairwell applications
  - » 3 Year Limited Warranty
  - » See Finish Disclaimer on page 200

Item No.	Type	Size	Watt	Lumens
8161-615BL	Wall Mount	7"W x 10.75"H x 8" Ext.	14W LED (Incl.)	405
8162-615BL	Wall Mount	9"W x 14"H x 10.25" Ext.	14W LED (Incl.)	528
8164-615BL	Chain Hung	9"L x 9"W x 13.25"H	14W LED (Incl.)	550
8166-615BL	Post Mount	9"L x 9"W x 14.5"H	14W LED (Incl.)	436

# Seneca Square LED



LED



72221-571-L

LED



72222-571-L

Finish:  
Whisper Bronze

Glass:  
Clear Seeded Glass

Features:

- » Aluminum Construction
- » 14W, 2,700K LED Incl., CRI 80
- » Hand Applied Multi-Step Finish
- » 3 Year Limited Warranty
- » See Finish Disclaimer on page 200

Item No.	Type	Size	Watt	Lumens
72221-571-L	Wall Mount	5.75"W x 9"H x 7.25" Ext.	14W LED (Incl.)	417
72222-571-L	Wall Mount	5.75"W x 13.25"H x 7.25" Ext.	14W LED (Incl.)	393

LED

# Eastborne LED



72401-287B-L

Downlight



72402-287B-L

Downlight

LED

LED

**Finish:**

Sand Bronze with Gold Highlights

**Glass:**

Frosted White Glass

**Features:**

- » Aluminum Construction
- » 12W and 20W, 3,000K LED (Incl.), CRI 98
- » California Title 24 Compliant
- » Hand Applied Multi-Step Finish
- » 3 Year Limited Warranty
- » See Finish Disclaimer on page 200

Item No.	Type	Size	Watt	Lumens
72401-287B-L	Wall Mount	7"W x 13.25"H x 4.5" Ext.	12W LED (Incl.)	547
72402-287B-L	Wall Mount	7"W x 17.25"H x 4.5" Ext.	20W LED (Incl.)	744

# Lynhaven LED



1245-246-L

LED



1246-246-L

LED

Finish:  
Alder Bronze

Glass:  
Mitered White Glass

- Features:
- » Aluminum Construction
  - » 14W and 19W, 3,000K LED Incl., CRI 97
  - » Indoor / Outdoor
  - » Hand Applied Multi-Step Finish
  - » 3 Year Limited Warranty
  - » See Finish Disclaimer on page 200

LED

Item No.	Type	Size	Watt	Lumens
1245-246-L	Wall Mount	5"W x 10"H x 4.5" Ext.	14W LED (Incl.)	570
1246-246-L	Wall Mount	5"W x 14"H x 4.5" Ext.	19W LED (Incl.)	739

# Everton Rain LED



72399-615B-L

**NEW**

Finish:  
Dorian Bronze™

Glass:  
Rain Glass

Features:

- » Aluminum Construction
- » Open Top/Open Bottom
- » 14W, 3,000K LED (Incl.), CRI 80
- » 3 Year Limited Warranty
- » See Finish Disclaimer on page 200

Item No.	Type	Size	Watt	Lumens	Notes
72399-615B-L	Pocket Lantern	7.5"W x 14.5"H x 3.75" Ext.	14W LED (Incl.)	979	ADA Compliant

**DARK-SKY**



72400-615B-L



**NEW**

Finish:  
Dorian Bronze™

Features:

- » Cast Aluminum Construction
- » Closed Top/Open Bottom
- » IDA-Approved™
- » 14W, 3,000K LED (Incl.), CRI 91
- » Also available:  
Dorian Bronze™ - Dark Sky, page 147
- » 3 Year Limited Warranty
- » See Finish Disclaimer on page 200

Item No.	Type	Size	Watt	Lumens	Notes
72400-615B-L	Pocket Lantern	7"W x 4.75"H x 3.75" Ext.	14W LED (Incl.)	384	ADA Compliant

# Holbrook LED



8153-568-L



Canopy Detail

8154-568-L



8151-568-L



8152-568-L

Finish:  
Forged Stone Silver

Glass:  
Etched Opal Glass

- Features:
- » Aluminum Construction
  - » 14W, 2,700K LED (Incl.), CRI 80
  - » Hand Applied Multi-Step Finish
  - » Rod Hung Style can also be used for interior foyer or stairwell applications
  - » 3 Year Limited Warranty
  - » See Finish Disclaimer on page 200

Item No.	Type	Size	Watt	Lumens
8151-568-L	Wall Mount	5"W x 12.5"H x 6.25"Ext.	14W LED (Incl.)	615
8152-568-L	Wall Mount	5"W x 14.5"H x 6.25"Ext.	14W LED (Incl.)	618
8153-568-L	Wall Mount	5"W x 18"H x 6.25"Ext.	14W LED (Incl.)	677
8154-568-L	Rod Hung	5" Dia. x 10.75"H Adjustable to 58.25"H Max.	14W LED (Incl.)	688

# Bay View™ LED



LED



9801-143-L



9802-143-L



9802-144-L



9801-144-L

LED

Finish:  
Brushed Stainless Steel  
Oil Rubbed Bronze

Glass:  
Etched Opal Glass

Features:

- » Stainless Steel Construction
- » Ideal for areas with harsh weather conditions
- » 14W and 19W, 2700K LED (Incl.), CRI 80
- » Also available:
  - Brushed Stainless Steel - Incandescent, page 122
  - Oil Rubbed Bronze - Incandescent, page 122
  - Brushed Stainless Steel - Fluorescent, page 176
  - Oil Rubbed Bronze - Fluorescent, page 176
- » 3 Year Limited Warranty
- » See Finish Disclaimer on page 200

## STAINLESS STEEL

Item No.	Type	Size	Watt	Lumens	Notes
9801-143-L	Pocket Lantern	7"W x 9.5"H x 4" Ext.	14W LED (Incl.)	333	ADA Compliant
9801-144-L	Pocket Lantern	7"W x 9.5"H x 4" Ext.	14W LED (Incl.)	333	ADA Compliant
9802-143-L	Pocket Lantern	7.75"W x 12"H x 4.5" Ext.	19W LED (Incl.)	723	
9802-144-L	Pocket Lantern	7.75"W x 12"H x 4.5" Ext.	19W LED (Incl.)	723	

# Skyline LED



72502-A144-L

Finish:  
Brushed Aluminum  
Dorian Bronze™

Glass:  
Metal Shade

- Features:
- » Aluminum Construction
  - » 11W, 2700K LED (Incl.), CRI 80
  - » Indoor / Outdoor
  - » Also available:  
Brushed Aluminum - Fluorescent, page 175  
Dorian Bronze™ - Fluorescent, page 175
  - » 3 Year Limited Warranty
  - » See Finish Disclaimer on page 200



72501-615B-L



LED



72501-A144-L



72502-615B-L

LED

Item No.	Type	Size	Watt	Lumens	Notes
72501-615B-L	Wall Mount	5"W x 7.5"H x 4" Ext.	1-11W LED (Incl.)	320	ADA Compliant Closed Top/Open Bottom
72501-A144-L	Wall Mount	5"W x 7.5"H x 4" Ext.	1-11W LED (Incl.)	320	ADA Compliant Closed Top/Open Bottom
72502-615B-L	Wall Mount	5"W x 14.5"H x 4" Ext.	2-11W LED (Incl.)	610	ADA Compliant
72502-A144-L	Wall Mount	5"W x 14.5"H x 4" Ext.	2-11W LED (Incl.)	610	ADA Compliant



# Garreston Pointe **LED**



72440-291-L



72441-291-L

Finish:  
Architectural Bronze with Copper Highlights

Glass:  
Clear Seeded Glass  
Frosted Seeded Glass

- Features:
- » Aluminum Construction
  - » 14W, 2,700K LED Incl., CRI 80
  - » Hand Applied Multi-Step Finish
  - » 3 Year Limited Warranty
  - » See Finish Disclaimer on page 200

**LED**

Item No.	Type	Size	Watt	Lumens
72440-291-L	Wall Mount	6"W x 12"H x 6" Ext.	14W LED (Incl.)	472
72441-291-L	Wall Mount	6"W x 14.5"H x 6" Ext.	14W LED (Incl.)	472

# INCANDESCENT

---



*Minka Lavery® and The Great Outdoors® proudly present one of the largest selections of incandescent outdoor lighting in the industry. Built using state of the art manufacturing processes such as die cast aluminum, hand-crafted aluminum, solid brass and steel, these fixtures offer the highest quality workmanship and superior performance. Additionally, our Ever-Pro™ Series offers an exceptional extended warranty. The wide selection of products, style and finishes guarantees the perfect outdoor lighting to beautify your home.*

# Bexley Manor



37.75"  
Overall Height

9323-585

**NEW**

Finish:  
Black with Gold Highlights

Glass:  
Clear Beveled Glass

Features:

- » Cast Aluminum Construction
- » Chain Hung Style can also be used for interior foyer or stairwell applications
- » See Finish Disclaimer on page 200

Item No.	Type	Size	Watt	Notes
9323-585	Wall Mount	13"W x 37.75"H x 15.25"Ext.	6-40W Candelabra Base	

# Bexley Manor



9321-585



9324-585

**NEW**

Finish:  
Black with Gold Highlights

Glass:  
Clear Beveled Glass

**Features:**

- » Cast Aluminum Construction
- » Chain Hung Style can also be used for interior foyer or stairwell applications
- » See Finish Disclaimer on page 200

Item No.	Type	Size	Watt	Notes
9321-585	Wall Mount	9"W x 25.25"H x 11.25" Ext.	4-40W Candelabra Base	
9322-585	Wall Mount	11"W x 31.75"H x 13.5" Ext.	4-40W Candelabra Base	
9324-585	Chain Hung	13"L x 13"W x 37.75"H	6-40W Candelabra Base	
9326-585	Post Mount	11"L x 11"W x 32.5"H	4-40W Candelabra Base	

# Bexley Manor



9326-585



9322-585

# Rue Vieille



9312-586



9316-586



9313-586

**NEW**

Finish:  
Forged Bronze

Glass:  
Clear Seeded Glass

- Features:
- » Aluminum Construction
  - » Hand Applied Multi-Step Finish
  - » Chain Hung Style can also be used for interior foyer or stairwell applications
  - » See Finish Disclaimer on page 200

Item No.	Type	Size	Watt	Notes
9312-586	Wall Mount	8.75"W x 24"H x 11.25" Ext.	4-40W Candelabra Base	
9313-586	Wall Mount	10.75"W x 29"H x 13.75" Ext.	5-40W Candelabra Base	
9316-586	Post Mount	8.75"L x 8.75"W x 23.5"H	4-40W Candelabra Base	

# Rue Vieille



9311-586



9314-586

**NEW**

Finish:  
Forged Bronze

Glass:  
Clear Seeded Glass

Features:

- » Aluminum Construction
- » Hand Applied Multi-Step Finish
- » Chain Hung Style can also be used for interior foyer or stairwell applications
- » See Finish Disclaimer on page 200

Item No.	Type	Size	Watt	Notes
9311-586	Wall Mount	7"W x 17"H x 8.25" Ext.	1-100W Medium Base	
9314-586	Chain Hung	8.5"L x 8.5"W x 22"H	4-40W Candelabra base	





SOLID BRASS



72427-212

Finish:  
English Brass

Glass:  
Clear Seeded Glass

Features:

- » Solid Brass Construction
- » Chain Hung Style can also be used for interior foyer or stairwell applications
- » Chemical Finish
- » Family accepts CFL candelabra or medium base bulbs (Not Incl.)
- » See Finish Disclaimer on page 200

SOLID BRASS

Item No.	Type	Size	Watt	Notes
72427-212	Wall Mount	12"W x 26"H x 14" Ext.	4-60W Candelabra Base	Hinged Door

# Edenshire



SOLID BRASS



72423-212



72425-212

SOLID BRASS



72421-212

SOLID BRASS

Finish:  
English Brass

Glass:  
Clear Seeded Glass

Features:

- » Solid Brass Construction
- » Chain Hung Style can also be used for interior foyer or stairwell applications
- » Chemical Finish
- » Family accepts CFL candelabra or medium base bulbs (Not Incl.)
- » See Finish Disclaimer on page 200

Item No.	Type	Size	Watt	Notes
72420-212	Pocket Lantern	8.25"W x 15.5"H x 4.75" Ext.	2-60W Candelabra Base	Hinged Door
72421-212	Wall Mount	6"W x 14"H x 7.75" Ext.	1-60W Medium Base	Hinged Door
72422-212	Wall Mount	8.25"W x 18.75"H x 10" Ext.	3-60W Candelabra Base	Hinged Door
72423-212	Wall Mount	10"W x 22.25"H x 12" Ext.	4-60W Candelabra Base	Hinged Door
72424-212	Chain Hung	8.25"L x 8.25"W x 18.5"H	3-60W Candelabra Base	Hinged Door
72425-212	Chain Hung	12"L x 12"W x 26"H	4-60W Candelabra Base	Hinged Door
72426-212	Post Mount	8.25"L x 8.25"W x 19"H	3-60W Candelabra Base	Hinged Door

# Edenshire

SOLID  
BRASS



72424-212



72420-212

SOLID BRASS




72426-212



72422-212

SOLID BRASS

# Copperton



COPPER




9071-264



9072-264

COPPER



COPPER

COPPER



9073-264

COPPER

Finish:  
Manhattan Copper

Glass:  
Clear Glass

- Features:
- » Solid Copper Construction
  - » Decorative Burner Top
  - » Multi-Step Chemical Finish
  - » Copper Candle Sleeves
  - » Family accepts CFL candelabra bulbs (Not Incl.)
  - » See Finish Disclaimer on page 200

Item No.	Type	Size	Watt	Notes
9071-264	Pocket Lantern	7"W x 18.25"H x 6" Ext.	2-60W Candelabra Base	Hinged Door
9072-264	Wall Mount	6.75"W x 18.25"H x 7.5" Ext.	2-60W Candelabra Base	Hinged Door
9073-264	Pocket Lantern	9.75"W x 18.5"H x 6" Ext.	3-60W Candelabra Base	Hinged Door



SOLID BRASS



72434-261



72436-261

SOLID BRASS



72431-261



72432-261

SOLID BRASS



SOLID BRASS



72433-261

Finish:  
Colonial Brass

Glass:  
Clear Glass

- Features:
- » Solid Brass Construction
  - » Brass Candle Sleeves
  - » Chain Hung Style can also be used for interior foyer or stairwell applications
  - » Family accepts CFL candelabra or medium base bulbs (Not Incl.)
  - » See Finish Disclaimer on page 200

SOLID BRASS

Item No.	Type	Size	Watt	Notes
72431-261	Wall Mount	7"W x 14.5"H x 8.25" Ext.	1-100W Medium Base	
72432-261	Wall Mount	9"W x 19.5"H x 9.5" Ext.	4-60W Candelabra Base	Hinged Door
72433-261	Wall Mount	10.75"W x 21.5"H x 10.5" Ext.	4-60W Candelabra Base	Hinged Door
72434-261	Chain Hung	9"L x 7.5"W x 18.5"H	4-60W Candelabra base	Hinged Door
72436-261	Post Mount	9"L x 7.5"W x 22.25"H	4-60W Candelabra Base	Hinged Door

# Stratford Hall™



9091-95



5'-3"  
Overall Height

Finish:  
Heritage™ with Gold Highlights

Glass:  
Clear Beveled Glass

**Features:**

- » Cast Aluminum Construction
- » Metal Candle Sleeves
- » Hand Applied Multi-Step Finish
- » Chain Hung Style can also be used for interior foyer or stairwell applications
- » Family accepts CFL candelabra or medium base bulbs (Not Incl.)
- » See Finish Disclaimer on page 200

Item No.	Type	Size	Watt	Notes
8933-95	Wall Mount	17.75"W x 40"H x 21.25" Ext.	5-40W Candelabra Base	© 1999 Minka Lighting, Inc.
8934-95	Chain Hung	18.5" Dia. x 30" H	5-40W Candelabra Base	© 1999 Minka Lighting, Inc.
8935-95	Post Mount	12.25" Dia. x 23.5" H	2-60W Candelabra Base	© 1999 Minka Lighting, Inc.
9091-95	Wall Mount	25.5"W x 63.25"H x 31.5" Ext.	9-60W Candelabra Base	© 1999 Minka Lighting, Inc.





8934-95



8935-95



8933-95

# Stratford Hall™



8932-95



8930-95



8936-95

# Stratford Hall™



8937-95



9094-95



8931-95

Finish:  
Heritage™ with Gold Highlights

Glass:  
Clear Beveled Glass

- Features:
- » Cast Aluminum Construction
  - » Metal Candle Sleeves
  - » Hand Applied Multi-Step Finish
  - » Chain Hung Style can also be used for interior foyer or stairwell applications
  - » Family accepts CFL candelabra or medium base bulbs (Not Incl.)
  - » See Finish Disclaimer on page 200

Item No.	Type	Size	Watt	Notes
8930-95	Wall Mount	8"W x 20.75"H x 11.25" Ext.	1-100W Medium Base	© 1999 Minka Lighting, Inc.
8931-95	Wall Mount	12.25"W x 25.25"H x 14.5" Ext.	2-60W Candelabra Base	© 1999 Minka Lighting, Inc.
8932-95	Wall Mount	13.75"W x 33.5"H x 16.75" Ext.	4-40W Candelabra Base	© 1999 Minka Lighting, Inc.
8936-95	Post Mount	14.25" Dia. x 28" H	4-40W Candelabra Base	© 1999 Minka Lighting, Inc.
8937-95	Wall Mount	8"W x 15.00"H x 11.75" Ext.	1-100W Medium Base	© 1999 Minka Lighting, Inc.
9094-95	Chain Hung	25.5" Dia x 46" H	9-60W Candelabra Base	© 1999 Minka Lighting, Inc.



8693-66

Finish:  
Black

Glass:  
Clear Beveled Glass

**Features:**

- » Cast Aluminum Construction
- » Metal Candle Sleeves
- » Hand Applied Finish
- » Chain Hung Style can also be used for interior foyer or stairwell applications
- » Family accepts CFL candelabra or medium base bulbs (Not Incl.)
- » Also available:
  - » Vintage Rust™ - Incandescent, page 61
  - » Vintage Rust™ - Fluorescent, page 164
- » See Finish Disclaimer on page 200

Item No.	Type	Size	Watt	Notes
8691-66	Wall Mount	7.75"W x 21"H x 10.25" Ext.	2-60W Candelabra Base	
8692-66	Wall Mount	10"W x 27.75"H x 13.25" Ext.	3-60W Candelabra Base	
8693-66	Wall Mount	12"W x 32.25"H x 16" Ext.	4-60W Candelabra Base	
8696-66	Post Mount	10"L x 10"W x 25"H	3-60W Candelabra Base	
8697-66	Pocket Lantern	7.5"W x 14.75"H x 4.75" Ext.	1-100W Medium Base	



8697-66



8691-66



8692-66



8696-66



8694-66



8698-66



8690-66



8695-66

Finish:  
Black

Glass:  
Clear Beveled Glass

Features:

- » Cast Aluminum Construction
- » Metal Candle Sleeves
- » Hand Applied Finish
- » Chain Hung Style can also be used for interior foyer or stairwell applications
- » Family accepts CFL candelabra or medium base bulbs (Not Incl.)

» Also available:

Vintage Rust™ - Incandescent, page 61

Vintage Rust™ - Fluorescent, page 164

» See Finish Disclaimer on page 200

Item No.	Type	Size	Watt	Notes
8690-66	Wall Mount	6.25"W x 11.5"H x 8" Ext.	1-100W Medium Base	
8694-66	Chain Hung	12"L x 12"W x 28.75"H	4-40W Candelabra Base	
8695-66	Post Mount	7.5"L x 7.5"W x 20"H	3-40W Candelabra Base	
8698-66	Pocket Lantern	10"W x 18.75"H x 6.5" Ext.	3-40W Candelabra Base	



8693-61

Finish:  
Vintage Rust™

Glass:  
Clear Beveled Glass

Features:

- » Cast Aluminum Construction
- » Metal Candle Sleeves
- » Hand Applied Multi-Step Finish
- » Chain Hung Style can also be used for interior foyer or stairwell applications
- » Family accepts CFL candelabra or medium base bulbs (Not Incl.)
- » Also available:
  - Black - Incandescent, page 58
  - Vintage Rust™ - Fluorescent, page 164
- » See Finish Disclaimer on page 200

Item No.	Type	Size	Watt	Notes
8693-61	Wall Mount	12"W x 32.25"H x 16" Ext.	4-60W Candelabra Base	



8691-61



8694-61



8692-61



8696-61





8697-61



8698-61



8695-61



8690-61

Finish:  
Vintage Rust™

Glass:  
Clear Beveled Glass

**Features:**

- » Cast Aluminum Construction
- » Metal Candle Sleeves
- » Hand Applied Multi-Step Finish
- » Chain Hung Style can also be used for interior foyer or stairwell applications
- » Family accepts CFL candelabra or medium base bulbs (Not Incl.)
- » Also available:
  - Black - Incandescent, page 58
  - Vintage Rust™ - Fluorescent, page 164
- » See Finish Disclaimer on page 200

Item No.	Type	Size	Watt	Notes
8690-61	Wall Mount	6.25"W x 11.5"H x 8" Ext.	1-100W Medium Base	
8691-61	Wall Mount	7.75"W x 21"H x 10.25" Ext.	2-60W Candelabra Base	
8692-61	Wall Mount	10"W x 27.75"H x 13.25" Ext.	3-60W Candelabra Base	
8694-61	Chain hung	12"L x 12"W x 28.75"H	4-40W Candelabra Base	
8695-61	Post Mount	7.5"L x 7.5"W x 20"H	3-40W Candelabra Base	
8696-61	Post Mount	10"L x 10"W x 25"H	3-60W Candelabra Base	
8697-61	Pocket Lantern	7.5"W x 14.75"H x 4.75" Ext.	1-100W Medium Base	
8698-61	Pocket Lantern	10"W x 18.75"H x 6.5" Ext.	3-40W Candelabra Base	



8997-66



8990-66



8995-66



8991-66



8992-66



9909-1-66

Finish:  
Black

Glass:  
Mouth Blown Clear Hammered Glass

**Features:**

- » Cast Aluminum Construction
- » Metal Candle Sleeves
- » Hand Applied Finish
- » Family accepts CFL candelabra or medium base bulbs (Not Incl.)
- » Also available:  
  - » Vintage Rusti™ - Incandescent, page 66
  - » Vintage Rusti™ - Fluorescent, page 160
- » See Finish Disclaimer on page 200

Item No.	Type	Size	Watt	Notes
8990-66	Wall Mount	7.75"W x 19.75"H x 12.5" Ext.	1-100W Medium Base	© 2000 Minka Lighting, Inc.
8991-66	Wall Mount	9.5"W x 25"H x 14.75" Ext.	2-60W Candelabra Base	© 2000 Minka Lighting, Inc.
8992-66	Wall Mount	12"W x 31.5"H x 18.5" Ext.	3-60W Candelabra Base	© 2000 Minka Lighting, Inc.
8995-66	Post Mount	9.5" Dia. x 23.75"H	2-60W Candelabra Base	© 2000 Minka Lighting, Inc.
8997-66	Wall Mount	7.75"W x 17.5"H x 9.5" Ext.	1-100W Medium base	© 2000 Minka Lighting, Inc.
9909-1-66	Flush Mount	11.75" Dia. x 8.5"H	2-40W Candelabra Base	© 2000 Minka Lighting, Inc.



8992-61

Finish:  
Vintage Rust™

Glass:  
Mouth Blown Clear Hammered Glass

**Features:**

- » Cast Aluminum Construction
- » Metal Candle Sleeves
- » Hand Applied Multi-Step Finish
- » Chain Hung Style can also be used for interior foyer or stairwell applications
- » Family accepts CFL candelabra or medium base bulbs (Not Incl.)

» Also available:

- Black - Incandescent, page 64
- Vintage Rust™ - Fluorescent, page 160
- » See Finish Disclaimer on page 200

Item No.	Type	Size	Watt	Notes
8991-61	Wall Mount	9.5"W x 25"H x 14.75" Ext.	2-60W Candelabra Base	© 2000 Minka Lighting, Inc.
8992-61	Wall Mount	12"W x 31.5"H x 18.5" Ext.	3-60W Candelabra Base	© 2000 Minka Lighting, Inc.
8994-61	Chain Hung	15" Dia. x 35.5"H	5-60W Candelabra Base	© 2000 Minka Lighting, Inc.
8997-61	Wall Mount	7.75"W x 17.5"H x 9.5" Ext.	1-100W Medium Base	



8997-61



8994-61



8991-61



8996-61



8990-61



8995-61

Finish:  
Vintage Rust™

Glass:  
Mouth Blown Clear Hammered Glass

Features:

- » Cast Aluminum Construction
- » Metal Candle Sleeves
- » Hand Applied Multi-Step Finish
- » Chain Hung Style can also be used for interior foyer or stairwell applications
- » Family accepts CFL candelabra or medium base bulbs (Not Incl.)

» Also available:

Black - Incandescent, page 64

Vintage Rust™ - Fluorescent, page 160

» See Finish Disclaimer on page 200

Item No.	Type	Size	Watt	Notes
8990-61	Wall Mount	7.75"W x 19.75"H x 12.5" Ext.	1-100W Medium Base	© 2000 Minka Lighting, Inc.
8995-61	Post Mount	9.5" Dia. x 23.75"H	2-60W Candelabra Base	© 2000 Minka Lighting, Inc.
8996-61	Post Mount	12.25" Dia. x 28.75"H	3-60W Candelabra Base	© 2000 Minka Lighting, Inc.



8903-94

Finish:  
Heritage™

Glass:  
Mouth Blown Clear Optic Glass

**Features:**

- » Cast Aluminum Construction
- » Metal Candle Sleeves
- » Hand Applied Multi-Step Finish
- » Chain Hung Style can also be used for interior foyer or stairwell applications
- » Family accepts CFL candelabra bulbs (Not Incl.)
- » See Finish Disclaimer on page 200

Item No.	Type	Size	Watt	Notes
8903-94	Wall Mount	12"W x 34.25"H x 16.25" Ext.	4-40W Candelabra Base	



8902-94



8907-94

Finish:  
Heritage™

Glass:  
Mouth Blown Clear Optic Glass

- Features:
- » Cast Aluminum Construction
  - » Metal Candle Sleeves
  - » Hand Applied Multi-Step Finish
  - » Chain Hung Style can also be used for interior foyer or stairwell applications
  - » Family accepts CFL candelabra bulbs (Not Incl.)
  - » See Finish Disclaimer on page 200

Item No.	Type	Size	Watt	Notes
8901-94	Wall Mount	9.75"W x 27.75"H x 13.75" Ext.	3-40W Candelabra Base	
8902-94	Wall Mount	9.75"W x 27.75"H x 13.75" Ext.	3-40W Candelabra Base	
8904-94	Chain Hung	12" Dia. x 30.25"H	4-40W Candelabra Base	
8907-94	Wall Mount	6.75"W x 19.5"H x 9.75" Ext.	2-40W Candelabra Base	





8904-94



8901-94



8900-94



8908-94



Finish:  
Heritage™

Glass:  
Mouth Blown Clear Optic Glass

Features:

- » Cast Aluminum Construction
- » Metal Candle Sleeves
- » Hand Applied Multi-Step Finish
- » Chain Hung Style can also be used for interior foyer or stairwell applications
- » Family accepts CFL candelabra bulbs (Not Incl.)
- » See Finish Disclaimer on page 200

Item No.	Type	Size	Watt	Notes
8900-94	Wall Mount	6.75"W x 19.5"H x 9.75" Ext.	2-40W Candelabra Base	
8905-94	Wall Mount	6.75"W x 18.25"H x 7.75" Ext.	2-40W Candelabra Base	
8906-94	Post Mount	12" Dia. x 33"H	4-40W Candelabra Base	
8908-94	Wall Mount	12"W x 34.75"H x 16.75" Ext.	4-40W Candelabra Base	
8909-94	Post Mount	9.75" Dia. x 28"H	3-40W Candelabra Base	
9909-94	Flush Mount	11.75" Dia. x 9.75"H	2-40W Candelabra Base	



8905-94



9909-94



8909-94



8906-94

# Morgan Park™



8847-94



9909-94



8842-94

Finish:  
Heritage™

Glass:  
Mouth Blown Clear Optic Glass

**Features:**

- » Cast Aluminum Construction
- » Metal Candle Sleeves
- » Hand Applied Multi-Step Finish
- » Chain Hung Style can also be used for interior foyer or stairwell applications
- » Family accepts CFL candelabra or medium base bulbs (Not Incl.)
- » See Finish Disclaimer on page 200

Item No.	Type	Size	Watt	Notes
8840-94	Wall Mount	7.5"W x 17.5"H x 9.25" Ext.	1-100W Medium Base	
8841-94	Wall Mount	9.75"W x 26"H x 11" Ext.	2-60W Candelabra Base	
8842-94	Wall Mount	12.25"W x 32.75"H x 13.75" Ext.	3-60W Candelabra Base	
8844-94	Chain Hung	15" Dia. x 35.5"H	5-60W Candelabra Base	
8845-94	Post Mount	7.5" Dia. x 17.5" H	1-100W Medium Base	
8846-94	Post Mount	12.25" Dia. x 28.5"H	3-60W Candelabra Base	
8847-94	Wall Mount	7.5"W x 17.5"H x 9.25" Ext.	1-100W Medium Base	
9909-94	Flush Mount	11.75" Dia. x 9.75"H	2-40W Candelabra Base	

# Morgan Park™



8844-94



8841-94



8846-94



8840-94



8845-94





SOLID BRASS



8817-57



8815-57

SOLID BRASS



8810-57



8811-57



8816-57

SOLID BRASS

SOLID BRASS

Amherst™



8812-57

SOLID BRASS

Finish:  
Roman Bronze™

Glass:  
Mouth Blown Clear Seeded Glass

- Features:
- » Solid Brass Construction
  - » Hand Applied Multi-Step Finish
  - » Family accepts CFL candelabra or medium base bulbs (Not Incl.)
  - » See Finish Disclaimer on page 200

Item No.	Type	Size	Watt	Notes
8810-57	Wall Mount	6.75"W x 13"H x 8" Ext.	1-100W Medium Base	
8811-57	Wall Mount	9.75"W x 22.5"H x 11.75" Ext.	3-60W Candelabra Base	
8812-57	Wall Mount	12"W x 28"H x 14.5" Ext.	4-60W Candelabra Base	
8815-57	Wall Mount	9.75"W x 22"H x 11.5" Ext.	3-60W Candelabra Base	© 1998 Minka Lighting, Inc.
8816-57	Post Mount	12" Dia. x 24"H	4-60W Candelabra Base	
8817-57	Wall Mount	6.75"W x 16.75"H x 9.25" Ext.	1-100W Medium Base	



8761-166



8763-166

Finish:  
Corona Bronze™

Glass:  
Clear Hammered Glass

**Features:**

- » Cast Aluminum Construction
- » Metal Candle Sleeves
- » Chain Hung Style can also be used for interior foyer or stairwell applications
- » Family accepts CFL candelabra or medium base bulbs (Not Incl.)
- » Also available:
  - Black - LED, page 16
  - Corona Bronze™ - Fluorescent, page 172
- » See Finish Disclaimer on page 200

Item No.	Type	Size	Watt	Notes
8761-166	Wall Mount	6.25"W x 12.25"H x 7.75" Ext.	1-100W Medium Base	
8762-166	Wall Mount	8"W x 16.25"H x 9.5" Ext.	1-100W Medium Base	
8763-166	Wall Mount	10"W x 20"H x 12" Ext.	3-60W Candelabra Base	
8764-166	Chain Hung	10" Dia. x 18.25"H	3-60W Candelabra Base	
8765-166	Post Mount	10" Dia. x 23"H	3-60W Candelabra Base	
8766-166	Post Mount	8" Dia. x 19.25"H	1-100W Medium Base	
8769-166	Flush Mount	13" Dia. x 7.25"H	2-60W Medium Base	





8764-166



8769-166



8762-166



8765-166



8766-166

# Taylor Court™



8613-A61



8614-A61



8619-A61



8616-A61



8612-A61



8617-A61



8611-A61

Finish:  
Vintage Rust™

Glass:  
Clear Seeded Glass

**Features:**

- » Aluminum Construction
- » Metal Candle Sleeves
- » Hand Applied Multi-Step Finish
- » Chain Hung Style can also be used for interior foyer or stairwell applications
- » Family accepts CFL candelabra or medium base bulbs (Not Incl.)
- » See Finish Disclaimer on page 200

Item No.	Type	Size	Watt	Notes
8611-A61	Wall Mount	6.5"W x 12.75"H x 8.25" Ext.	1-60W Medium Base	
8612-A61	Wall Mount	8"W x 17.5"H x 10.25" Ext.	2-60W Candelabra Base	
8613-A61	Wall Mount	10.25"W x 22.75"H x 12.75" Ext.	3-60W Candelabra Base	
8614-A61	Chain Hung	10.25" Dia. x 18.75"H	3-60W Candelabra Base	
8616-A61	Post Mount	10.25" Dia. x 19.25"H	3-60W Candelabra Base	
8617-A61	Wall Mount	12.5"W 28.25"H x 15" Ext.	3-60W Candelabra Base	
8619-A61	Flush Mount	11" Dia. x 6.5"H	2-40W Candelabra Base	

# Kent Place™



9144-407



9143-407



9142-407



9146-407



9147-407



9141-407

Item No.	Type	Size	Watt	Notes
9141-407	Wall Mount	7"W x 15.75"H x 10" Ext.	2-60W Candelabra Base	U.S. Patent(s): D511,396; D512,174; D512,176; D515,237
9142-407	Wall Mount	9"W x 20.25"H x 12.75" Ext.	3-60W Candelabra Base	U.S. Patent(s): D511,396; D512,174; D512,176; D515,237
9143-407	Wall Mount	10.25"W x 23.5"H x 14.75" Ext.	3-60W Candelabra Base	U.S. Patent(s): D511,396; D512,174; D512,176; D515,237
9144-407	Chain Hung	10.25" Dia. x 21.75"H	3-60W Candelabra Base	U.S. Patent(s): D512,176; D515,237
9146-407	Post Mount	10.25" Dia. x 22.25"H	3-60W Candelabra Base	U.S. Patent(s): D512,176; D515,237
9147-407	Wall Mount	12"W x 28"H x 17.5" Ext.	4-60W Candelabra Base	U.S. Patent(s): D511,396; D512,174; D512,176; D515,237

Finish:  
Prussian Gold™

Glass:  
Clear Seeded Glass

**Features:**

- » Cast Aluminum Construction
- » Metal Candle Sleeves
- » Hand Applied Multi-Step Finish
- » Family accepts CFL candelabra (Not Incl.)
- » Also available:  
Prussian Gold™ - Fluorescent, page 162
- » See Finish Disclaimer on page 200



9018-66



9011-66



9010-66



9016-66



Finish:  
Black

Glass:  
Bent Clear Seeded Glass

**Features:**

- » Cast Aluminum Construction
- » Metal Candle Sleeves
- » Family accepts CFL candelabra or medium base bulbs (Not Incl.)
- » See Finish Disclaimer on page 200

Item No.	Type	Size	Watt	Notes
9010-66	Wall Mount	6.75"W x 13.75"H x 9.5" Ext.	1-100W Medium Base	
9011-66	Wall Mount	8.5"W x 17.5"H x 11.5" Ext.	3-60W Candelabra Base	
9016-66	Post Mount	8.5" Dia. x 21.5"H	3-60W Candelabra Base	
9018-66	Wall Mount	8.5"W x 23.25"H x 11.5" Ext.	3-60W Candelabra Base	

# Vista Montaire



73003-143C



73001-143C

**Finish:**  
Oil Rubbed Bronze with Gold Highlights

**Glass:**  
Clear Water Glass

- Features:**
- » Aluminum Construction
  - » Metal Candle Sleeves
  - » Polished Brass Reflector
  - » Family accepts CFL candelabra base bulbs (Not Incl.)
  - » See Finish Disclaimer on page 200

Item No.	Type	Size	Watt	Notes
73001-143C	Pocket Lantern	7"W x 14"H x 4"Ext	1-60W Candelabra Base	Hinged Door, ADA Compliant
73003-143C	Pocket Lantern	9.5"W x 17.5"H x 5.5" Ext.	3-60W Candelabra Base	Hinged Door

# Irvington Manor



72171-189



72173-189

Finish:  
Chelesa Bronze™

Glass:  
Clear Seeded Glass

**Features:**

- » Aluminum Construction
- » Metal Candle Sleeves
- » Chain Hung Style can also be used for interior foyer or stairwell applications
- » Family accepts CFL candelabra or medium base bulbs (Not Incl.)
- » See Finish Disclaimer on page 200

Item No.	Type	Size	Watt	Notes
72170-189	Pocket Lantern	8.5"W x 19"H x 7" Ext.	2-60W Candelabra Base	Hinged Door Stainless Steel Reflector
72171-189	Wall Mount	6.5"W x 12"H x 7.5" Ext.	1-60W Medium Base	
72172-189	Wall Mount	8.5"W x 16.75"H x 9.5" Ext.	3-60W Candelabra Base	
72173-189	Wall Mount	10.5"W x 20.75"H x 11.75" Ext.	4-60W Candelabra Base	
72174-189	Chain Hung	8.5"L x 8.5"W x 15.5"H	3-60W Candelabra Base	
72176-189	Post Mount	8.5"L x 8.5"W x 18"H	3-60W Candelabra Base	



# Irvington Manor

ALUMINUM



72174-189



72172-189



72176-189



72170-189



8268-161



8263-161



8262-161



8266-161



8265-161



8264-161



8267-161



8261-161

Finish:  
Mossoro Walnut™ with Silver Highlights

Glass:  
Clear Glass

- Features:
- » Aluminum Construction
  - » Metal Candle Sleeves
  - » Hand Applied Multi-Step Finish
  - » Chain Hung Style can also be used for interior foyer or stairwell applications
  - » Family accepts CFL candelabra or medium base bulbs (Not Incl.)
  - » Also available:  
    Black - LED page 26
  - » See Finish Disclaimer on page 200

Item No.	Type	Size	Watt	Notes
8261-161	Wall Mount	5.75"W x 14.25"H x 7" Ext.	1-60W Candelabra Base	
8262-161	Wall Mount	7.75"W x 17.75"H x 9" Ext.	2-60W Candelabra Base	
8263-161	Wall Mount	9.75"W x 22.75"H x 11.25 Ext.	3-60W Candelabra Base	
8264-161	Chain Hung	9.75"L x 9.75"W x 19"H	3-60W Candelabra Base	
8265-161	Post Mount	11.5"L x 11.5"W x 23.25"H	4-60W Candelabra Base	
8266-161	Post Mount	7.75"L x 7.75"W x 16.75"H	2-60W Candelabra Base	
8267-161	Wall Mount	11.5"W x 26.75"H x 13.25" Ext.	4-60W Candelabra Base	
8268-161	Chain Hung	11.5"L x 11.5"W x 22"H	4-60W Candelabra Base	

# Sunnybrook



72522-246



72524-246



72521-246



72526-246



72523-246

**NEW**

Finish:  
Alder Bronze

Glass:  
Clear Seeded Glass

Features:

- » Aluminum Construction
- » Hand Applied Multi-Step Finish
- » Chain Hung Style can also be used for interior foyer or stairwell applications
- » See Finish Disclaimer on page 200

Item No.	Type	Size	Watt	Notes
72521-246	Wall Mount	6.5"W x 11.25"H x 7.5" Ext.	1-100W Medium Base	
72522-246	Wall Mount	8.5"W x 17.25"H x 10" Ext.	3-60W Candelabra Base	
72523-246	Wall Mount	10"W x 19.25"H x 11.5" Ext.	4-60W Candelabra Base	
72524-246	Chain Hung	8.5"L x 8.5"W x 12.25"H	4-60W Candelabra base	
72526-246	Post Mount	8.5"L x 8.5"W x 16.25"H	4-60W Candelabra Base	

# Hawks Point



72531-143



72534-143



72532-143



72536-143

# Hawks Point



72533-143

**NEW**

Finish:  
Oil Rubbed Bronze

Glass:  
Clear Seeded Glass

Item No.	Type	Size	Watt	Notes
72531-143	Wall Mount	6.5"W x 11.75"H x 6" Ext.	1-100W Medium Base	
72532-143	Wall Mount	8.5"W x 15"H x 8.5" Ext.	2-60W Candelabra Base	
72533-143	Wall Mount	9.5"W x 16.5"H x 9.5" Ext.	4-60W Candelabra Base	
72534-143	Chain Hung	8.5"L x 6.5"W x 13"H	2-60W Candelabra base	
72536-143	Post Mount	8.5"L x 6.5"W x 17"H	2-60W Candelabra Base	

Features:

- » Aluminum Construction
- » Hand Applied Multi-Step Finish
- » Chain Hung Style can also be used for interior foyer or stairwell applications
- » See Finish Disclaimer on page 200

# Rivendale Court



72301-291



72302-291



72306-291



# Rivendale Court



72303-291

Finish:  
Architectural Bronze with Copper Highlights

Glass:  
Clear Glass

Features:  
 » Aluminum Construction with Cast Elements  
 » Metal Candle Sleeves  
 » Family accepts CFL candelabra or medium base bulbs (Not Incl.)  
 » See Finish Disclaimer on page 200

Item No.	Type	Size	Watt	Notes
72301-291	Wall Mount	8.5"W x 14.75"H x 8.25" Ext.	1-100W Medium Base	
72302-291	Wall Mount	10.5"W x 19"H x 10.25" Ext.	3-60W Candelabra Base	
72303-291	Wall Mount	13.75"W x 23.25"H x 13.25" Ext.	4-60W Candelabra Base	
72306-291	Post Mount	9.5"L x 9.5"W x 20.25"H	3-60W Candelabra Base	

# Astrapia II



72542-593



72544-593



72546-593



72540-593-L

# Astrapia II



72543-593



72541-593

**NEW**

Finish:  
Dark Rubbed Sienna with Aged Silver

Glass:  
Clear Seeded Glass

**Features:**

- » Cast Aluminum Construction
- » Metal Candle Sleeves
- » Hand Applied Multi-Step Finish
- » Chain Hung Style can also be used for interior foyer or stairwell applications
- » Family accepts CFL candelabra (Not Incl.)
- » See Finish Disclaimer on page 200

Item No.	Type	Size	Watt	Notes
72540-593-L	Pocket Lantern	9.5"W x 19.75"H x 5" Ext.	16W LED (Incl.)	3 Year Limited Warranty
72541-593	Wall Mount	7"W x 19.75"H x 8.75" Ext.	2-60W Candelabra Base	
72542-593	Wall Mount	9"W x 23.25"H x 11.25" Ext.	3-60W Candelabra Base	
72543-593	Wall Mount	11"W x 28.5"H x 13.5" Ext.	4-60W Candelabra Base	
72544-593	Chain Hung	11"L x 11"W x 23.75"H	4-60W Candelabra Base	
72546-593	Post Mount	11"L x 11"W x 20.75"H	4-60W Candelabra Base	



72512-246



72514-246



72511-246



72516-246



72513-246

**NEW**

Finish:  
Alder Bronze

Glass:  
Clear Water Glass

Item No.	Type	Size	Watt	Notes
72511-246	Wall Mount	6"W x 11.25"H x 7" Ext.	1-60W Medium Base	
72512-246	Wall Mount	8"W x 14.5"H x 9" Ext.	4-60W Candelabra Base	
72513-246	Wall Mount	9.75"W x 17.25"H x 10.75" Ext.	4-60W Candelabra Base	
72514-246	Chain Hung	8"L x 8"W x 15"H	4-60W Candelabra Base	
72516-246	Post Mount	8"L x 8"W x 15.75"H	4-60W Candelabra Base	

- Features:
- » Aluminum Construction
  - » Hand Applied Multi-Step Finish
  - » Chain Hung Style can also be used for interior foyer or stairwell applications
  - » See Finish Disclaimer on page 200

# Crossroads Point



9281-171



9282-171



9286-171

# Crossroads Point



9283-171

Finish:  
Architectural Bronze

Glass:  
Clear Glass

- Features:
- » Aluminum Construction with Cast Elements
  - » Metal Candle Sleeves
  - » Family accepts CFL candelabra or medium base bulbs (Not Incl.)
  - » See Finish Disclaimer on page 200

Item No.	Type	Size	Watt	Notes
9281-171	Wall Mount	6.5"W x 14.5"H x 7.25" Ext.	1-60W Candelabra Base	
9282-171	Wall Mount	8.5"W x 19.25"H x 9.5" Ext.	2-60W Candelabra Base	
9283-171	Wall Mount	10.5"W x 23.5"H x 12" Ext.	4-60W Candelabra Base	
9286-171	Post Mount	8.5"L x 8.5"W x 19.5"H	3-60W Candelabra Base	

# Wilshire Park



72112-149



72114-149



72111-149



72116-149



# Wilshire Park



72113-149

Finish:  
Portsmouth Bronze

Glass:  
Clear Water Glass

**Features:**

- » Aluminum Construction
- » Metal Candle Sleeves
- » Hand Applied Multi-Step Finish
- » Chain Hung Style can also be used for interior foyer or stairwell applications
- » Family accepts CFL candelabra or medium base bulbs (Not Incl.)
- » See Finish Disclaimer on page 200

Item No.	Type	Size	Watt	Notes
72111-149	Wall Mount	6.25"W x 13.75"H x 6.25" Ext.	1-100W Medium Base	
72112-149	Wall Mount	8"W x 18.5"H x 8.75" Ext.	3-60W Candelabra Base	
72113-149	Wall Mount	9.75"W x 22"H x 10.75" Ext.	4-40W Candelabra Base	
72114-149	Chain Hung	8"L x 6.5"W x 16"H	3-60W Candelabra Base	
72116-149	Post Mount	8"L x 6.5"W x 18.75"H	3-60W Candelabra Base	

# Oxford Road



72294-291



72292-291



72291-291

Finish:  
Architectural Bronze with Copper Highlights

Glass:  
Clear Water Glass

- Features:
- » Aluminum Construction
  - » Metal Candle Sleeves
  - » Chain Hung Style can also be used for interior foyer or stairwell applications
  - » Family accepts CFL candelabra or medium base bulbs (Not Incl.)
  - » See Finish Disclaimer on page 200

Item No.	Type	Size	Watt	Notes
72291-291	Wall Mount	8.5"W x 13.25"H x 9.5" Ext.	1-60W Medium Base	
72292-291	Wall Mount	11"W x 17"H x 12" Ext.	4-60W Candelabra Base	
72294-291	Chain Hung	11"L x 11"W x 17"H	4-60W Candelabra Base	



8883-A39

Finish:  
Spanish Iron™

Glass:  
Champagne Hammered Glass

Features:

- » Handcrafted Aluminum Construction
- » Metal Candle Sleeves
- » Hand Applied Multi-Step Finish
- » Chain Hung Style can also be used for interior foyer or stairwell applications
- » Family accepts CFL candelabra or medium base bulbs (Not Incl.)
- » Also available:
  - Spanish Iron™ - Fluorescent, page 166
  - Vintage Rust™ - Incandescent, page 109
- » See Finish Disclaimer on page 200

Item No.	Type	Size	Watt	Notes
8883-A39	Wall Mount	12.5"W x 41.25"H x 16.5" Ext.	5-60W Candelabra Base	



8884-A39



8881-A39

Finish:  
Spanish Iron™

Glass:  
Champagne Hammered Glass

**Features:**

- » Handcrafted Aluminum Construction
- » Metal Candle Sleeves
- » Hand Applied Multi-Step Finish
- » Chain Hung Style can also be used for interior foyer or stairwell applications
- » Family accepts CFL candelabra or medium base bulbs (Not Incl.)
- » Also available:
  - Spanish Iron™ - Fluorescent, page 166
  - Vintage Rust™ - Incandescent, page 109
- » See Finish Disclaimer on page 200

Item No.	Type	Size	Watt	Notes
8881-A39	Wall Mount	8.75"W x 28.75"H x 11.5" Ext.	2-60W Candelabra Base	
8882-A39	Wall Mount	10.5"W x 34.25"H x 13.5" Ext.	4-60W Candelabra Base	
8884-A39	Chain Hung	12.75" Dia. x 32"H	5-60W Candelabra Base	
8886-A39	Post Mount	10.5" Dia. x 26"H	4-60W Candelabra Base	
8887-A39	Pocket Lantern	10.5"W x 19.5"H x 5.5" Ext.	2-60W Candelabra Base	



8887-A39



8886-A39



8882-A39



8880-A39



8889-A39



8885-A39

Finish:  
Spanish Iron™

Glass:  
Champagne Hammered Glass

Features:

- » Handcrafted Aluminum Construction
- » Metal Candle Sleeves
- » Hand Applied Multi-Step Finish
- » Chain Hung Style can also be used for interior foyer or stairwell applications
- » Family accepts CFL candelabra or medium base bulbs (Not Incl.)
- » Also available:
  - Spanish Iron™ - Fluorescent, page 166
  - Vintage Rust™ - Incandescent, page 109
- » See Finish Disclaimer on page 200

Item No.	Type	Size	Watt	Notes
8880-A39	Wall Mount	7.75"W x 16"H x 10" Ext.	1-100W Medium Base	
8885-A39	Post Mount	9" Dia. x 22.5"H	3-60W Candelabra Base	
8889-A39	Flush Mount	12.75" Dia. x 7"H	3-40W Candelabra Base	



8883-A61

**Finish:**  
Vintage Rust™ Powder Coat

**Glass:**  
Champagne Hammered Glass

- Features:**
- » Handcrafted Aluminum Construction
  - » Metal Candle Sleeves
  - » Hand Applied Multi-Step Finish
  - » Chain Hung Style can also be used for interior foyer or stairwell applications
  - » Family accepts CFL candelabra or medium base bulbs (Not Incl.)
  - » Also available:
    - Spanish Iron™ - Incandescent, page 105
    - Spanish Iron™ - Fluorescent, page 166
  - » See Finish Disclaimer on page 200

Item No.	Type	Size	Watt	Notes
8883-A61	Wall Mount	12.5"W x 41.25"H x 16.5" Ext.	5-60W Candelabra Base	



8880-A61



8889-A61



8887-A61



8881-A61

Finish:  
Vintage Rust™ Powder Coat

Glass:  
Champagne Hammered Glass

- Features:
- » Handcrafted Aluminum Construction
  - » Metal Candle Sleeves
  - » Hand Applied Multi-Step Finish
  - » Chain Hung Style can also be used for interior foyer or stairwell applications
  - » Family accepts CFL candelabra or medium base bulbs (Not Incl.)
  - » Also available:
    - Spanish Iron™ - Incandescent, page 105
    - Spanish Iron™ - Fluorescent, page 166
  - » See Finish Disclaimer on page 200

Item No.	Type	Size	Watt	Notes
8880-A61	Wall Mount	7.75"W x 16"H x 10" Ext.	1-100W Medium Base	
8881-A61	Wall Mount	8.75"W x 28.75"H x 11.5" Ext.	2-60W Candelabra Base	
8882-A61	Wall Mount	10.5"W x 34.25"H x 13.5" Ext.	4-60W Candelabra Base	
8884-A61	Chain Hung	12.75" Dia. x 32"H	5-60W Candelabra Base	
8885-A61	Post Mount	9" Dia. x 22.5"H	3-60W Candelabra Base	
8887-A61	Pocket Lantern	10.5"W x 19.5"H x 5.5" Ext.	2-60W Candelabra Base	
8889-A61	Flush Mount	12.75" Dia. x 7"H	3-40W Candelabra Base	





8884-A61



8882-A61



8885-A61



SOLID BRASS



8581-51



8582-51

SOLID BRASS

Finish:  
Rust

Glass:  
Clear Seeded Glass

Features:

- » Solid Brass Construction
- » Multi-Step Chemical Finish
- » Family accepts CFL candelabra or medium base bulbs (Not Incl.)
- » See Finish Disclaimer on page 200

Item No.	Type	Size	Watt	Notes
8581-51	Wall Mount	6.25"W x 14.75"H x 7.75" Ext.	1-100W Medium Base	
8582-51	Wall Mount	9"W x 20.5"H x 10.5" Ext.	3-60W Candelabra Base	



BRASS



8567-51



8562-51

BRASS



8560-51



8563-51



8561-51

BRASS

Finish:  
Rust

Glass:  
Clear Seeded Glass

- Features:
- » Brass Construction
  - » Hand Applied Chemical Finish
  - » Family accepts CFL candelabra or medium base bulbs (Not Incl.)
  - » See Finish Disclaimer on page 200

Item No.	Type	Size	Watt	Notes
8560-51	Pocket Lantern	10"W x 17.5"H x 5.25" Ext.	2-60W Candelabra Base	
8561-51	Wall Mount	6"W x 12.25"H x 7.75" Ext.	1-100W Medium Base	
8562-51	Wall Mount	8.25"W x 16.5"H x 9.75" Ext.	3-60W Candelabra Base	
8563-51	Wall Mount	10"W x 19"H x 11.5" Ext.	4-60W Candelabra Base	
8567-51	Column Mount	11.5"L x 11.5"W x 18.75"H	4-60W Candelabra Base	

# Willow Pointe



Finish:  
Chelsea Bronze™

Glass:  
Clear Seeded Glass

Features:

- » Aluminum Construction
- » Metal Candle Sleeves
- » Chain Hung Style can also be used for interior foyer or stairwell applications
- » Family accepts CFL candelabra or medium base bulbs (Not Incl.)
- » See Finish Disclaimer on page 200

73093-189

Item No.	Type	Size	Watt	Notes
73091-189	Wall Mount	7"W x 13.75"H x 6.75" Ext.	1-60W Medium Base	
73092-189	Wall Mount	9"W x 19"H x 7.25" Ext.	2-60W Candelabra Base	
73093-189	Wall Mount	11"W x 22"H x 8.75" Ext.	4-60W Candelabra Base	
73094-189	Chain Hung	9"L x 6.25"W x 15"H	2-60W Candelabra Base	
73096-189	Post Mount	9"L x 6.25"W x 17"H	3-60W Candelabra Base	

# Willow Pointe

ALUMINUM



73092-189



73094-189



73091-189



73096-189

# Downtown Edison



71163-143C



71163-A144

Finish:  
Brushed Aluminum  
Oil Rubbed Bronze with Gold Highlights

Glass:  
Clear Glass

- Features:
- » Aluminum Construction
  - » Family accepts CFL medium base bulbs. (Not Incl.)
  - » See Minka-lavery® catalog for complete section of complementary fixtures and accessories
  - » See Finish Disclaimer on page 200

Item No.	Type	Size	Watt	Notes
71163-143C	Wall Mount	8.5"W x 13"H x 11.5" Ext.	1-100W Medium Base	
71163-A144	Wall Mount	8.5"W x 13"H x 11.5" Ext.	1-100W Medium Base	



71167-91



71166-91

Finish:  
Antique Bronze

Features:

- » Functional Bulb Guard
- » Hand Applied Multi-Step Finish
- » Family accepts CFL medium base bulbs (Not Incl.)
- » See Finish Disclaimer on page 200

Item No.	Type	Size	Watt	Notes
71166-91	Wall Mount	6.25"W x 9"H x 6.5" Ext.	1-60W Medium Base	G25 Bulb Pictured
71167-91	Wall Mount	8.25"W x 10.25"H x 8.5" Ext.	1-100W Medium Base	G25 Bulb Pictured

# Spyglass Cove



72262-189



72261-189

Finish:  
Chelesa Bronze™

Glass:  
Mouth Blown Clear Seeded Glass

Features:

- » Aluminum Construction
- » Multi-Step Painted Finish
- » Family accepts CFL medium base bulbs (Not Incl.)
- » See Finish Disclaimer on page 200

Item No.	Type	Size	Watt	Notes
72261-189	Wall Mount	9"W x 14.25"H x 11.5" Ext.	1-100W Medium Base	
72262-189	Wall Mount	12"W x 18.5"H x 14.75" Ext.	1-100W Medium Base	

# Settlers Way



72161-179



72164-179



72166-179





72162-179

Finish:  
Textured French Bronze

Glass:  
Clear Seeded Glass

- Features:
- » Aluminum Construction
  - » Hand Applied Multi-Step Finish
  - » Chain Hung Style can also be used for interior foyer or stairwell applications
  - » Family accepts CFL candelabra or medium base bulbs (Not Incl.)
  - » See Finish Disclaimer on page 200

Item No.	Type	Size	Watt	Notes
72161-179	Wall Mount	7.75"W x 15.25"H x 9" Ext.	1-60W Candelabra Base	
72162-179	Wall Mount	9.5"W x 17.5"H x 11" Ext.	1-100W Medium Base	
72164-179	Chain Hung	9.5" Dia. x 18.5"H	1-100W Medium Base	Open Bottom
72166-179	Post Mount	9.5" Dia. x 17.75"H	1-100W Medium Base	

# Lynnfield



72234-143C



72233-143C

Finish:  
Oil Rubbed Bronze with Gold Highlights

Glass:  
Ribbed Clear Seeded Glass

- Features:
- » Aluminum Construction
  - » Metal Candle Sleeves
  - » Open Bottom
  - » Chain Hung Style can also be used for interior foyer or stairwell applications
  - » Family accepts CFL candelabra or medium base bulbs (Not Incl.)
  - » See Finish Disclaimer on page 200

Item No.	Type	Size	Watt	Notes
72231-143C	Wall Mount	5"W x 11.5"H x 5.75" Ext.	1-60W Medium Base	
72232-143C	Wall Mount	6.25"W x 16.5"H x 7.25" Ext.	1-100W Medium Base	
72233-143C	Wall Mount	8"W x 18.75"H x 9.25" Ext.	3-60W Candelabra Base	
72234-143C	Chain Hung	6.25" Dia. x 16"H	1-100W Medium Base	
72236-143C	Post Mount	6.25" Dia. x 17.75"H	1-100W Medium Base	



72232-143C



72236-143C



72231-143C

# Bay View™



STAINLESS STEEL



9803-144



9803-143

Finish:  
Brushed Stainless Steel  
Oil Rubbed Bronze

Glass:  
Etched Opal Glass

- Features:
- » Stainless Steel Construction
  - » Ideal for areas with harsh weather conditions
  - » Family accepts CFL medium base bulbs (Not Incl.)
  - » Also available:
    - Brushed Stainless Steel - LED, page 37
    - Oil Rubbed Bronze - LED, page 37
    - Brushed Stainless Steel - Fluorescent, page 176
    - Oil Rubbed Bronze - Fluorescent, page 176
  - » See Finish Disclaimer on page 200

STAINLESS STEEL

Item No.	Type	Size	Watt	Notes
9801-143	Pocket Lantern	7"W x 9.5"H x 4" Ext.	1-60W Medium Base	ADA Compliant
9801-144	Pocket Lantern	7"W x 9.5"H x 4" Ext.	1-60W Medium Base	ADA Compliant
9802-143	Pocket Lantern	7.75"W x 12"H x 4.5" Ext.	2-60W Medium Base	
9802-144	Pocket Lantern	7.75"W x 12"H x 4.5" Ext.	2-60W Medium Base	
9803-143	Pocket Lantern	8"W x 20"H x 4.5" Ext.	2-60W Medium Base	
9803-144	Pocket Lantern	8"W x 20"H x 4.5" Ext.	2-60W Medium Base	
9806-143	Post Mount	8" Dia. x 12.5"H	1-100W Medium Base	
9806-144	Post Mount	8" Dia. x 12.5"H	1-100W Medium Base	

STAINLESS STEEL

Bay View™



9802-144



9802-143



9801-144

STAINLESS STEEL



9806-144



9806-143



9801-143



STAINLESS STEEL

# Delshire Point



9812-166



9813-166



9811-166

Finish:  
Corona Bronze™

Glass:  
Cream Linen Glass

**Features:**

- » Cast Aluminum Construction
- » Hand Applied Multi-Step Finish
- » Family accepts CFL medium base bulbs (Not Incl.)
- » See Finish Disclaimer on page 200

Item No.	Type	Size	Watt	Notes
9811-166	Pocket Lantern	5.5"W x 8.25"H x 4" Ext.	1-60W Medium Base	ADA Compliant
9812-166	Pocket Lantern	6.5"W x 12"H x 4" Ext.	1-60W Medium Base	ADA Compliant
9813-166	Pocket Lantern	8.5"W x 15.5"H x 5.25" Ext.	2-60W Medium Base	

# STAINLESS STEEL

# Vista Delmar



72192-144



72191-144

Finish:  
Brushed Stainless Steel

Glass:  
Etched Opal Glass

**Features:**

- » Stainless Steel Construction
- » Family accepts CFL medium base bulbs (Not Incl.)
- » Ideal for Harsh Weather
- » See Finish Disclaimer on page 200

Item No.	Type	Size	Watt	Notes
72191-144	Wall Mount	6.75"W x 13"H x 5.5" Ext.	1-100W Medium Base	
72192-144	Wall Mount	8.75"W x 18.5"H x 6.75" Ext.	1-100W Medium Base	

# STAINLESS STEEL

# Colva



72122-144-PL



72121-144-PL

Finish:  
Brushed Stainless Steel

Glass:  
Etched Glass

**Features:**

- » Stainless Steel Construction
- » California Title 24 Compliant
- » Compact Fluorescent Bulbs (Incl.)
- » See Finish Disclaimer on page 200

Item No.	Type	Size	Watt	Notes
72121-144-PL	Pocket Lantern	6.5"W x 12.25"H x 4" Ext.	1-13W GU24 Spiral CFL (Incl.)	Title 24 ADA Compliant
72122-144-PL	Pocket Lantern	10.25"W x 18"H x 4" Ext.	2-13W GU24 Spiral CFL (Incl.)	Title 24 ADA Compliant



## DARK-SKY

72383-246



Finish:  
Alder Bronze

Glass:  
Clear Seeded Glass

Features:

- » Aluminum Construction
- » Recessed Light Source
- » IDA-Approved™
- » See Finish Disclaimer on page 200

## DARK-SKY

Item No.	Type	Size	Watt	Notes
72381-246	Wall Mount	4.75"W x 13"H x 4.25" Ext.	1-35W GU10 Halogen Base (Incl.)	
72382-246	Wall Mount	7"W x 15.75"H x 4.5" Ext.	1-35W GU10 Halogen Base (Incl.)	
72383-246	Wall Mount	9"W x 20"H x 4.5" Ext.	2-35W GU10 Halogen Base (Incl.)	





DARK-SKY



72382-246



72381-246

DARK-SKY



72371-615B



72372-615B

Finish:  
Dorian Bronze™

Glass:  
Brushed Aluminum Center Accent

Features:  
» Aluminum Construction  
» See Finish Disclaimer on page 200

Item No.	Type	Size	Watt	Notes
72371-615B	Pocket Lantern	6"W x 14"H x 3" Ext.	2-35W GU10 Halogen Base (Incl.)	ADA Compliant
72372-615B	Pocket Lantern	8"W x 17.25"H x 3" Ext.	4-35W GU10 Halogen Base (Incl.)	ADA Compliant

# Casona Square



72343-615B



72342-615B

Finish:  
Dorian Bronze™

Glass:  
Etched White Opal Glass

Features:  
» Aluminum Construction  
» See Finish Disclaimer on page 200

Item No.	Type	Size	Watt	Notes
72342-615B	Wall Mount	8"W x 13"H x 4.25" Ext.	1-40W G9 Xenon (Incl.)	
72343-615B	Wall Mount	8"W x 18"H x 4.25" Ext.	1-40W G9 Xenon (Incl.)	

# Addison Park



72313-615B



72311-615B



72312-615B

Finish:  
Dorian Bronze™

Glass:  
Etched Opal Glass

**Features:**

- » Aluminum Construction
- » Family accepts CFL medium base bulbs (Not Incl.)
- » See Finish Disclaimer on page 200

Item No.	Type	Size	Watt	Notes
72311-615B	Wall Mount	5.75"W x 10"H x 6.75" Ext.	1-100W Medium Base	
72312-615B	Wall Mount	7"W x 12.5"H x 8" Ext.	1-100W Medium Base	
72313-615B	Wall Mount	9.5"W x 16.25"H x 10.5" Ext.	1-100W Medium Base	

# Travessa



72331-291



72332-291



72336-291

Finish:  
Architectural Bronze with Copper Highlights

Glass:  
Clear Crackle Glass

- Features:
- » Aluminum Construction
  - » Metal Candle Sleeves
  - » Family accepts CFL candelabra or medium base bulbs (Not Incl.)
  - » See Finish Disclaimer on page 200

Item No.	Type	Size	Watt	Notes
72331-291	Wall Mount	7"W x 11"H x 6.5" Ext.	1-100W Medium Base	
72332-291	Wall Mount	9.5"W x 16.5"H x 8.75" Ext.	3-60W Candelabra Base	
72336-291	Post Mount	7.75" Dia. x 16.25"H	3-60W Candelabra Base	

# Ladera



73063-246

Finish:  
Alder Bronze

Glass:  
Clear Glass

**Features:**

- » Aluminum Construction
- » Chain Hung Style can also be used for interior foyer or stairwell applications
- » Family accepts CFL medium base bulbs (Not Incl.)
- » See Finish Disclaimer on page 200

Item No.	Type	Size	Watt	Notes
73061-246	Wall Mount	6.25"W x 14.5"H x 5.5" Ext.	1-40W Ferro Medium Base	
73062-246	Wall Mount	7.5"W x 16.5"H x 7.25" Ext.	1-40W Ferro Medium Base	
73063-246	Wall Mount	8.75" x 18.5"H x 7.5" Ext.	1-40W Ferro Medium Base	
73064-246	Chain Hung	7.5"L x 6"W x 15.75"H	1-40W Ferro Medium Base	
73066-246	Post Mount	7.5"L x 6"W x 18"H	1-40W Ferro Medium Base	



73061-246

73064-246



73062-246

73066-246



# Abbey Lane™



9152-A357



9154-A357



9156-A357



9151-A357





9153-A357

Finish:  
Iron Oxide

Glass:  
Mouth Blown Clear Seeded Glass

**Features:**

- » Aluminum Construction
- » Metal Candle Sleeves
- » Hand Applied Multi-Step Finish
- » Chain Hung Style can also be used for interior foyer or stairwell applications
- » Family accepts CFL candelabra or medium base bulbs (Not Incl.)
- » Also available:  
    Iron Oxide - Fluorescent, page 170
- » See Finish Disclaimer on page 200

Item No.	Type	Size	Watt	Notes
9151-A357	Wall Mount	7"W x 10"H x 9.5" Ext.	1-60W Medium Base	
9152-A357	Wall Mount	9"W x 12.5"H x 11" Ext.	2-60W Candelabra Base	
9153-A357	Wall Mount	11"W x 14.5"H x 12.75" Ext.	3-60W Candelabra Base	
9154-A357	Chain Hung	11" Dia. x 16.25"H	3-60W Candelabra Base	
9156-A357	Post Mount	9" Dia. x 17"H	2-60W Candelabra Base	

# Harveston Manor



8729-A615B



8723-A615B

Finish:  
Dorian Bronze™

Glass:  
Double French Scavo Glass

**Features:**

- » Aluminum Construction
- » Metal Candle Sleeves
- » Hand Applied Multi-Step Finish
- » Chain Hung Style can also be used for interior foyer or stairwell applications
- » Family accepts CFL candelabra or medium base bulbs (Not Incl.)
- » See Finish Disclaimer on page 200

Item No.	Type	Size	Watt	Notes
8721-A615B	Wall Mount	7.25"W x 9"H x 8.25" Ext.	1-60W Medium Base	
8722-A615B	Wall Mount	9"W x 14.75"H x 10.75" Ext.	1-100W Medium Base	
8723-A615B	Wall Mount	11"W x 18.25"H x 12.5" Ext.	3-60W Candelabra Base	
8724-A615B	Chain Hung	11" Dia. x 16.5"H	3-60W Candelabra Base	
8725-A615B	Column Mount	11" Dia. x 16"H	3-60W Candelabra Base	
8726-A615B	Post Mount	9" Dia. x 13.75"H	1-100W Medium Base	
8729-A615B	Flush Mount	11.25" Dia. x 5"H	2-60W Medium Base	

# Harveston Manor

ALUMINUM



8724-A615B



8722-A615B



8721-A615B



8725-A615B



8726-A615B



8717-66



8718-66



8718-91



8717-91

Finish:  
Antique Bronze  
Black

Glass:  
Textured Etched Glass

**Features:**

- » Cast Aluminum Construction
- » Powder Coat Finish
- » Family accepts CFL candelabra or medium base bulbs (Not Incl.)
- » See Finish Disclaimer on page 200

Item No.	Type	Size	Watt	Notes
8717-66	Wall Mount	6"W x 14.5"H x 6.75" Ext.	1-100W Medium Base	
8717-91	Wall Mount	6"W x 14.5"H x 6.75" Ext.	1-100W Medium Base	
8718-66	Wall Mount	8"W x 18.25"H x 9" Ext.	2-60W Candelabra Base	
8718-91	Wall Mount	8"W x 18.25"H x 9" Ext.	2-60W Candelabra Base	



8252-61



8252-94



8251-94



8256-61



8256-94



8251-61

Finish:  
Heritage™  
Vintage Rust™

Glass:  
One Piece Clear Driftwood Glass

- Features:
- » Cast Aluminum Construction
  - » Hand Applied Multi-Step Finish
  - » Closed Bottom
  - » Family accepts CFL medium base bulbs (Not Incl.)
  - » Also available:  
Heritage™ - Fluorescent, page 183  
Vintage Rust™ - Fluorescent, page 180
  - » See Finish Disclaimer on page 200

Item No.	Type	Size	Watt	Notes
8251-61	Wall Mount	6.5"W x 8.75"H x 8" Ext.	1-100W Medium Base	
8251-94	Wall Mount	6.5"W x 8.75"H x 8" Ext.	1-100W Medium Base	
8252-61	Wall Mount	8.5"W x 12.75"H x 10.75" Ext.	1-100W Medium Base	
8252-94	Wall Mount	8.5"W x 12.75"H x 10.75" Ext.	1-100W Medium Base	
8256-61	Post Mount	8.5" Dia. x 14.75"H	1-100W Medium Base	
8256-94	Post Mount	8.5" Dia. x 14.75"H	1-100W Medium Base	



8202-94



8202-61



8201-94



8201-61



8206-94



8206-61

Finish:  
Heritage™  
Vintage Rust™

Glass:  
One Piece Clear Optic Glass

- Features:
- » Cast Aluminum Construction
  - » Hand Applied Multi-Step Finish
  - » Family accepts CFL medium base bulbs (Not Incl.)
  - » Also available:  
Heritage™ - Fluorescent, page 179  
Vintage Rust™ - Fluorescent, page 179
  - » See Finish Disclaimer on page 200

Item No.	Type	Size	Watt	Notes
8201-61	Wall Mount	6.5"W x 14.25"H x 7.5" Ext.	1-100W Medium Base	U.S. Patent(s): D510,453; D512,793; D518,224
8201-94	Wall Mount	6.5"W x 14.25"H x 7.5" Ext.	1-100W Medium Base	U.S. Patent(s): D510,453; D512,793; D518,224
8202-61	Wall Mount	8.75"W x 17"H x 10.25" Ext.	1-100W Medium Base	U.S. Patent(s): D510,453; D512,793; D518,224
8202-94	Wall Mount	8.75"W x 17"H x 10.25" Ext.	1-100W Medium Base	U.S. Patent(s): D510,453; D512,793; D518,224
8206-61	Post Mount	8.75" Dia. x 17.25"H	1-100W Medium Base	U.S. Patent(s): D510,453
8206-94	Post Mount	8.75" Dia. x 17.25"H	1-100W Medium Base	U.S. Patent(s): D510,453



9067-66



9067-91



9060-91



9060-66



9066-66

Finish:  
Black  
Antique Bronze

Glass:  
Clear Seeded Glass

- Features:
- » Cast Aluminum Construction
  - » Hand Applied Finish
  - » Family accepts CFL medium base bulbs (Not Incl.)
  - » See Finish Disclaimer on page 200

Item No.	Type	Size	Watt	Notes
9060-66	Wall Mount	6"W x 16.5"H x 6.75" Ext.	1-100W Medium Base	
9060-91	Wall Mount	6"W x 16.5"H x 6.75" Ext.	1-100W Medium Base	
9066-66	Post Mount	7.25"L x 7.25"W x 16.75"H	1-100W Medium Base	
9067-66	Wall Mount	6"W x 16.5"H x 6.75" Ext.	1-100W Medium Base	
9067-91	Wall Mount	6"W x 16.5"H x 6.75" Ext.	1-100W Medium Base	

# DARK-SKY

The International Dark-Sky Association (IDA) is a non-profit organization that educates and promotes the reduction of the effects of outdoor lights on the night sky by reducing the night time glare caused by outdoor lighting fixtures. The Great Outdoors® is pleased to present exciting Dark-Sky Friendly® families of outdoor lighting, compliant with the standards established by the IDA, including our popular Dark-Sky Friendly® series of outdoor ceramic sconces. All meet UL or ETL standards for wet locations. While our Dark-Sky fixtures meet IDA specifications, you will need to consult local regulations for specific standards established in your area when choosing your fixtures.

## Features:

- Fully shielded light source reduces glare to enhance the night sky
- Attractive details allow Dark-Sky compliance without compromising style.





DARK-SKY

# Sage Ridge™



8282-A61



8284-A61



8283-A61

DARK-SKY



8286-A61



8281-A61

DARK-SKY

Finish:  
Vintage Rust™

Features:

- » Aluminum Construction
- » Recessed Light Source
- » Inspiring Grill Work
- » Hand Applied Multi-Step Finish
- » IDA-Approved™
- » Chain Hung Styles can also be used for interior foyer and stairwell applications
- » Family accepts most CFL medium base bulbs (Not Incl.)
- » See Finish Disclaimer on page 200

Item No.	Type	Size	Watt	Notes
8281-A61	Wall Mount	6.5"W x 12.75"H x 8.25" Ext.	1-60W Medium Base	A15 Bulb
8282-A61	Wall Mount	8.5"W x 16"H x 10.5" Ext.	1-60W Medium Base	
8283-A61	Wall Mount	10.5"W x 22.5"H x 12.75" Ext.	1-60W Medium Base	
8284-A61	Chain Hung	10.5" Dia. x 20"H	1-60W Medium Base	
8286-A61	Post Mount	8.5" Dia. x 19"H	1-60W Medium Base	



DARK-SKY



8101-A138



8102-A138

DARK-SKY

DARK-SKY



8106-A138

Finish:  
Aspen Bronze™

Glass:  
Metal Shade

- Features:
- » Aluminum Construction
  - » IDA-Approved™
  - » Family accepts CFL medium base bulbs (Not Incl.)
  - » Also available:
    - Aspen Bronze™ - LED, page 13
    - » See Finish Disclaimer on page 200

Item No.	Type	Size	Watt	Notes
8101-A138	Wall Mount	8.5" x 6"H x 10.5" Ext.	1-60W Medium Base	
8102-A138	Wall Mount	11"W x 6.5"H x 12.25" Ext.	1-60W Medium Base	
8106-A138	Post Mount	11.75"L x 8.5"W x 11"H	1-60W Medium Base	



## DARK-SKY



72212-A144



72211-A144

## DARK-SKY



72212-615B



72211-615B

Finish:  
Brushed Aluminum  
Dorian Bronze™

Glass:  
Metal Shade

- Features:
- » Aluminum Construction
  - » IDA-Approved™
  - » Family accepts CFL medium base bulbs (Not Incl.)
  - » See Finish Disclaimer on page 200

Item No.	Type	Size	Watt	Notes
72211-A144	Wall Mount	9"W x 8.25"H x 9.5" Ext.	1-60W Medium Base	
72211-615B	Wall Mount	9"W x 8.25"H x 9.5" Ext.	1-60W Medium Base	
72212-A144	Wall Mount	11"W x 10.5"H x 11.75" Ext.	1-100W Medium Base	
72212-615B	Wall Mount	11"W x 10.5"H x 11.75" Ext.	1-100W Medium Base	

# Vanira Place™



DARK-SKY



8122-A188-PL



REMOVABLE GLASS



8126-A188-PL



8121-A188-PL



REMOVABLE GLASS



REMOVABLE GLASS

DARK-SKY

DARK-SKY

Finish:  
Windsor Rust™

Glass:  
Double French Scavo Twist and Lock Glass

Features:

- » Aluminum Construction
- » IDA-Approved™
- » California Title 24 Compliant
- » Hand Applied Multi-Step Finish
- » Compact Fluorescent Bulbs (Incl.)
- » Removable glass for Full Cutoff Dark-Sky Application
- » See Finish Disclaimer on page 200

Item No.	Type	Size	Watt	Notes
8121-A188-PL	Wall Mount	9"W x 11"H x 11.75" Ext.	1-13W GU24 Spiral CFL (Incl.)	Title 24
8122-A188-PL	Wall Mount	12"W x 11.5"H x 14.75" Ext.	1-13W GU24 Spiral CFL (Incl.)	Title 24
8126-A188-PL	Post Mount	16"L x 12"W x 15.75"H	1-13W GU24 Spiral CFL (Incl.)	Title 24



72400-615B

Finish:  
Dorian Bronze™

- Features:
- » Cast Aluminum Construction
  - » Closed Top/Open Bottom
  - » IDA-Approved™
  - » See Finish Disclaimer on page 200

Item No.	Type	Size	Watt	Notes
72400-615B	Pocket Lantern	7.25"W x 4.75"H x 3.75" Ext.	2-35W GU10 Halogen	ADA Compliant Bulbs Incl.

# Ceramic



POCKET LANTERNS  
INDOOR/OUTDOOR



9838



9836

Finish:  
White Ceramic

- Features:
- » Carefree Ceramic Construction
  - » Closed Top/Open Bottom
  - » IDA-Approved™
  - » Family accepts CFL medium base bulbs (Not Incl.)
  - » See Finish Disclaimer on page 200

Item No.	Type	Size	Watt	Notes
9836	Pocket Lantern	8"W x 9.25"H x 5.5" Ext.	1-100W Medium Base	
9838	Pocket Lantern	7.25"W x 9"H x 4.25" Ext.	1-100W Medium Base	

DARK-SKY



## DARK-SKY



72321-247

## DARK-SKY



72322-247

Finish:  
Tinted Silver

Glass:  
Faceted Eidolon Krystal™ Glass

- Features:
- » Aluminum Construction
  - » Hand Applied Multi-Step Finish
  - » Recessed Light Source
  - » IDA-Approved™
  - » See Finish Disclaimer on page 200

## DARK-SKY

Item No.	Type	Size	Watt	Notes
72321-247	Wall Mount	4.75"W x 11"H x 3.5" Ext.	1-35W GU10 Halogen Base	ADA Compliant Halogen Bulb Incl.
72322-247	Wall Mount	4.75"W x 15"H x 3.5" Ext.	1-35W GU10 Halogen Base	ADA Compliant Halogen Bulb Incl.

# Artisan Lane



DARK-SKY



72251-66



72253-66



72252-66

DARK-SKY

Finish:  
Black

Glass:  
Clear Seeded Glass

Features:

- » Aluminum Construction
- » Recessed Light Source
- » IDA-Approved™
- » See Finish Disclaimer on page 200

Item No.	Type	Size	Watt	Notes
72251-66	Wall Mount	5.5"W x 13"H x 4.75" Ext. (Oval)	1-35W MR16 GU10 Halogen (Incl.)	
72252-66	Wall Mount	5.5"W x 18.5"H x 4.75" Ext. (Oval)	1-35W MR16 GU10 Halogen (Incl.)	
72253-66	Wall Mount	8.5"W x 23"H x 7.5" Ext. (Oval)	2-35W MR16 GU10 Halogen (Incl.)	

# COMPACT FLUORESCENT

---

*With designs ranging from Traditional to Contemporary, The Great Outdoors® by Minka Lavery® offers a wide variety of Compact Fluorescent (CFL) fixtures to meet any design need. Reducing energy consumption by up to 75% helps both you and our environment. In addition, our entire Compact Fluorescent collection complies with the strict California Title 24 requirements.*







71193-A357-PL

Finish:  
Iron Oxide

Glass:  
Double French Scavo Glass

Features:

- » Aluminum Construction
- » Hand Applied Multi-Step Finish
- » California Title 24 Compliant
- » Compact Fluorescent Bulbs (Incl.)
- » Chain Hung Styles can also be used for interior foyer and stairwell applications
- » See Finish Disclaimer on page 200

Item No.	Type	Size	Watt	Notes
71193-A357-PL	Wall Mount	10"W x 21.5"H x 12.5" Ext.	1-26W GU24 Spiral CFL (Incl.)	Title 24



71198-A357-PL



71194-A357-PL



71196-A357-PL



71197-A357-PL

Finish:  
Iron Oxide

Glass:  
Double French Scavo Glass

- Features:
- » Aluminum Construction
  - » Hand Applied Multi-Step Finish
  - » California Title 24 Compliant
  - » Compact Fluorescent Bulbs (Incl.)
  - » Chain Hung Styles can also be used for interior foyer and stairwell applications
  - » See Finish Disclaimer on page 200

Item No.	Type	Size	Watt	Notes
71190-A357-PL	Rod Hung	6"L x 6"W x 11"H Adjustable to 53"H Max.	1-13W GU24 Spiral CFL (Incl.)	Title 24
71191-A357-PL	Wall Mount	6"W x 12.25"H x 8" Ext.	1-13W GU24 Spiral CFL (Incl.)	Title 24
71192-A357-PL	Wall Mount	8"W x 17.5"H x 10" Ext.	1-13W GU24 Spiral CFL (Incl.)	Title 24
71194-A357-PL	Chain Hung	10"L x 10"W x 19.5"H	1-26W GU24 Spiral CFL (Incl.)	Title 24
71195-A357-PL	Post Mount	8"L x 8"W x 17.5"H	1-26W GU24 Spiral CFL (Incl.)	Title 24
71196-A357-PL	Post Mount	10.5"L x 10.5"W x 13.75"H	1-26W GU24 Spiral CFL (Incl.)	Title 24
71197-A357-PL	Pocket Lantern	6.5"W x 7.5"H x 5.75" Ext.	1-13W GU24 Spiral CFL (Incl.)	Title 24
71198-A357-PL	Pocket Lantern	10.5"W x 12"H x 6.25" Ext.	2-13W GU24 Spiral CFL (Incl.)	Title 24
71199-A357-PL	Flush Mount	10"L x 10"W x 7.25"H	2-13W GU24 Spiral CFL (Incl.)	Title 24



71192-A357-PL



71190-A357-PL



71199-A357-PL



71195-A357-PL

71191-A357-PL



# Lugarno Square



72012-A173-PL



72011-A173-PL



72016-A173-PL

Finish:  
Forged Silver

Glass:  
Etched White Glass

**Features:**

- » Cast Aluminum Construction
- » California Title 24 Compliant
- » Compact Fluorescent Bulbs (Incl.)
- » See Finish Disclaimer on page 200

Item No.	Type	Size	Watt	Notes
72011-A173-PL	Wall Mount	7.5"W x 14"H x 8.5" Ext.	1-13W GU24 Spiral CFL (Incl.)	Title 24 U.S. Patent(s): D586,493
72012-A173-PL	Wall Mount	9.25"W x 15.75"H x 9.25" Ext.	1-26W GU24 Spiral CFL (Incl.)	Title 24 U.S. Patent(s): D586,493
72016-A173-PL	Post Mount	9"L x 6.5"W x 17.25"H	1-26W GU24 Spiral CFL (Incl.)	Title 24 U.S. Patent(s): D586,493



8609-A179-PL



8603-A179-PL



8602-A179-PL



8605-A179-PL



8601-A179-PL

Finish:  
Textured French Bronze

Glass:  
Honey Opal Art Glass

- Features:
- » Aluminum Construction
  - » Closed Top/Open Bottom
  - » California Title 24 Compliant
  - » Compact Fluorescent Bulbs (Incl.)
  - » See Finish Disclaimer on page 200

Item No.	Type	Size	Watt	Notes
8601-A179-PL	Pocket Lantern	6"W x 7.5"H x 5" Ext.	1-13W GU24 Spiral CFL (Incl.)	Title 24
8602-A179-PL	Pocket Lantern	8"W x 11.75"H x 7" Ext.	1-13W GU24 Spiral CFL (Incl.)	Title 24
8603-A179-PL	Pocket Lantern	10"W x 13.5"H x 7" Ext.	1-13W GU24 Spiral CFL (Incl.)	Title 24
8605-A179-PL	Post Mount	8"L x 8"W x 13.25"H	1-13W GU24 Spiral CFL (Incl.)	Title 24
8609-A179-PL	Flush Mount	9.5"L x 9.5"W x 7"H	1-13W GU24 Spiral CFL (Incl.)	Title 24

# Andrita Court™



72029-A179-PL



72021-A179-PL



72020-A179-PL



72026-A179-PL



72022-A179-PL

# Andrita Court™



72023-A179-PL

Finish:  
Textured French Bronze

Glass:  
Pearl Mist Glass

- Features:
- » Aluminum Construction
  - » Hand Applied Multi-Step Finish
  - » California Title 24 Compliant
  - » Compact Fluorescent Bulbs (Incl.)
  - » See Finish Disclaimer on page 200

Item No.	Type	Size	Watt	Notes
72020-A179-PL	Pocket Lantern	7.5"W x 14.75"H x 4.75" Ext.	1-13W GU24 Spiral CFL (Incl.)	Title 24
72021-A179-PL	Pocket Lantern	9"W x 17.25"H x 5.5" Ext.	1-26W GU24 Spiral CFL (Incl.)	Title 24
72022-A179-PL	Wall Mount	6.25"W x 12.5"H x 8.75" Ext.	1-13W GU24 Spiral CFL (Incl.)	Title 24
72023-A179-PL	Wall Mount	7.5"W x 17.5"H x 10.75" Ext.	1-13W GU24 Spiral CFL (Incl.)	Title 24
72026-A179-PL	Post Mount	7.5" Dia. x 20"H	1-13W GU24 Spiral CFL (Incl.)	Title 24
72029-A179-PL	Flush Mount	11.5" Dia. x 4.75"H	1-26W GU24 Spiral CFL (Incl.)	Title 24

# Lander Heights™



9252-A199-PL



9251-A199-PL



9256-A199-PL



# Lander Heights™



9253-A199-PL

Finish:  
Forged Iron

Glass:  
Spanish Fire Piastra Glass

Features:

- » Aluminum Construction
- » Rustic Styling
- » California Title 24 Compliant
- » Compact Fluorescent Bulbs (Incl.)
- » See Finish Disclaimer on page 200

Item No.	Type	Size	Watt	Notes
9251-A199-PL	Wall Mount	6.5"W x 12.5"H x 8.75" Ext.	1-13W GU24 Spiral CFL (Incl.)	Title 24
9252-A199-PL	Wall Mount	9.25"W x 17.25"H x 11.75" Ext.	1-26W GU24 Spiral CFL (Incl.)	Title 24
9253-A199-PL	Wall Mount	11.5"W x 21.5"H x 14.75" Ext.	1-26W GU24 Spiral CFL (Incl.)	Title 24
9256-A199-PL	Post Mount	11.5" Dia. x 20.5"H	1-26W GU24 Spiral CFL (Incl.)	Title 24



8992-61-PL

Finish:  
Vintage Rust™

Glass:  
Double French Scavo Glass

Features:

- » Cast Aluminum Construction
- » Hand Applied Multi-Step Finish
- » California Title 24 Compliant
- » Compact Fluorescent Bulbs (Incl.)
- » Also available:
  - Black - Incandescent, page 64
  - Vintage Rust™ - Incandescent, page 66
- » See Finish Disclaimer on page 200

Item No.	Type	Size	Watt	Notes
8990-61-PL	Wall Mount	7.75"W x 19.75"H x 12.5" Ext.	1-13W GU24 Spiral CFL (Incl.)	Title 24 © 2000 Minka Lighting, Inc.
8991-61-PL	Wall Mount	9.5"W x 25"H x 14.75" Ext.	1-13W GU24 Spiral CFL (Incl.)	Title 24 © 2000 Minka Lighting, Inc.
8992-61-PL	Wall Mount	12"W x 31.5"H x 18.5" Ext.	1-26W GU24 Spiral CFL (Incl.)	Title 24 © 2000 Minka Lighting, Inc.
8995-61-PL	Post Mount	9.5" Dia. x 23.75"H	1-13W GU24 Spiral CFL (Incl.)	Title 24 © 2000 Minka Lighting, Inc.
8997-61-PL	Wall Mount	7.75"W x 17.5"H x 9.5" Ext.	1-13W GU24 Spiral CFL (Incl.)	Title 24



8997-61-PL



8990-61-PL



8995-61-PL



8991-61-PL



9143-407-PL

Finish:  
Prussian Gold™

Glass:  
Double French Scavo Glass

- Features:
- » Cast Aluminum Construction
  - » Hand Applied Multi-Step Finish
  - » California Title 24 Compliant
  - » Compact Fluorescent Bulbs (Incl.)
  - » Also available:
    - Prussian Gold™ - Incandescent, page 83
    - » See Finish Disclaimer on page 200

Item No.	Type	Size	Watt	Notes
9141-407-PL	Wall Mount	7"W x 15.75"H x 10" Ext.	1-13W GU24 Spiral CFL (Incl.)	Title 24 U.S. Patent(s): D511,396; D512,174; D512,176; D515,237
9142-407-PL	Wall Mount	9"W x 20.25"H x 12.75" Ext.	1-13W GU24 Spiral CFL (Incl.)	Title 24 U.S. Patent(s): D511,396; D512,174; D512,176; D515,237
9143-407-PL	Wall Mount	10.25"W x 23.5"H x 14.75" Ext.	1-26W GU24 Spiral CFL (Incl.)	Title 24 U.S. Patent(s): D511,396; D512,174; D512,176; D515,237
9146-407-PL	Post Mount	10.25" Dia. x 22.25"H	1-26W GU24 Spiral CFL (Incl.)	Title 24 U.S. Patent(s): D512,176; D515,237



9141-407-PL



9142-407-PL



9146-407-PL



8691-1-61-PL



8698-1-61-PL



8690-1-61-PL



8695-1-61-PL



8696-1-61-PL



8692-1-61-PL



8697-1-61-PL

Finish:  
Vintage Rust™

Glass:  
Double French Scavo Glass

**Features:**

- » Cast Aluminum Construction
- » Hand Applied Multi-Step Finish
- » California Title 24 Compliant
- » Compact Fluorescent Bulbs (Incl.)
- » Also available:
  - Black - Incandescent, page 58
  - Vintage Rust™ - Incandescent, page 61
- » See Finish Disclaimer on page 200

Item No.	Type	Size	Watt	Notes
8690-1-61-PL	Wall Mount	6.25"W x 11.5"H x 8" Ext.	1-13W GU24 Spiral CFL (Incl.)	Title 24
8691-1-61-PL	Wall Mount	7.75"W x 21"H x 10.25" Ext.	1-13W GU24 Spiral CFL (Incl.)	Title 24
8692-1-61-PL	Wall Mount	10"W x 27.75"H x 13.25" Ext.	1-26W GU24 Spiral CFL (Incl.)	Title 24
8695-1-61-PL	Post Mount	7.5"L x 7.5"W x 20"H	1-13W GU24 Spiral CFL (Incl.)	Title 24
8696-1-61-PL	Post Mount	10"L x 10"W x 25"H	1-26W GU24 Spiral CFL (Incl.)	Title 24
8697-1-61-PL	Pocket Lantern	7.5"W x 14.75"H x 4.75" Ext.	1-13W GU24 Spiral CFL (Incl.)	Title 24
8698-1-61-PL	Pocket Lantern	10"W x 18.75"H x 6.5" Ext.	1-26W GU24 Spiral CFL (Incl.)	Title 24



8882-A39-PL

Finish:  
Spanish Iron™

Glass:  
Double French Scavo Glass

Features:

- » Handcrafted Aluminum Construction
- » California Title 24 Compliant
- » Compact Fluorescent Bulbs (Incl.)
- » Also available:

Spanish Iron™ - Incandescent, page 105

Vintage Rust™ - Incandescent, page 109

» See Finish Disclaimer on page 200

Item No.	Type	Size	Watt	Notes
8880-A39-PL	Wall Mount	7.75"W x 16"H x 10" Ext.	1-13W GU24 Spiral CFL (Incl.)	Title 24
8881-A39-PL	Wall Mount	8.75"W x 28.75"H x 11.5" Ext.	1-13W GU24 Spiral CFL (Incl.)	Title 24
8882-A39-PL	Wall Mount	10.5"W x 34.25"H x 13.5" Ext.	1-26W GU24 Spiral CFL (Incl.)	Title 24
8885-A39-PL	Post Mount	9" Dia. x 22.5"H	1-13W GU24 Spiral CFL (Incl.)	Title 24
8887-A39-PL	Pocket Lantern	10.5"W x 19.5"H x 5.5" ext.	1-13W GU24 Spiral CFL (Incl.)	Title 24





8880-A39-PL



8887-A39-PL



8881-A39-PL



8885-A39-PL

# Chelesa Road™



9193-189-PL

Finish:  
Chelesa Bronze™

Glass:  
Double French Scavo Glass

**Features:**

- » Cast Aluminum Construction
- » California Title 24 Compliant
- » Compact Fluorescent Bulbs (Incl.)
- » Chain Hung Styles can also be used for interior foyer and stairwell applications
- » See Finish Disclaimer on page 200

Item No.	Type	Size	Watt	Notes
9190-189-PL	Pocket Lantern	8.5"W x 12.25"H x 4.5" Ext.	1-13W GU24 Spiral CFL (Incl.)	Title 24 © 2007 Minka Lighting, Inc.
9192-189-PL	Wall Mount	10.5"W x 22.5"H x 10.5" Ext.	1-13W GU24 Spiral CFL (Incl.)	Title 24 © 2007 Minka Lighting, Inc.
9193-189-PL	Wall Mount	13"W x 27.25"H x 13.25" Ext.	1-26W GU24 Spiral CFL (Incl.)	Title 24 © 2007 Minka Lighting, Inc.
9194-189-PL	Chain Hung	10.5"L x 8.5"W x 19.25"H	1-13W GU24 Spiral CFL (Incl.)	Title 24 © 2007 Minka Lighting, Inc.
9195-189-PL	Post Mount	10.5"L x 8.5"W x 20"H	1-13W GU24 Spiral CFL (Incl.)	Title 24 © 2007 Minka Lighting, Inc.

# Chelesa Road™



9190-189-PL




9194-189-PL



9192-189-PL



9195-189-PL



9151-A357-PL



9154-A357-PL



9156-A357-PL



9152-A357-PL



9153-A357-PL

Finish:  
Iron Oxide

Glass:  
Double French Scavo Glass

**Features:**

- » Aluminum Construction
- » Hand Applied Multi-Step Finish
- » California Title 24 Compliant
- » Compact Fluorescent Bulbs (Incl.)
- » Chain Hung Style can also be used for interior foyer or stairwell applications
- » Also available:
  - Iron Oxide - Incandescent, page 135
  - » See Finish Disclaimer on page 200

Item No.	Type	Size	Watt	Notes
9151-A357-PL	Wall Mount	7"W x 10"H x 9.5" Ext.	1-13W GU24 Spiral CFL (Incl.)	Title 24
9152-A357-PL	Wall Mount	9"W x 12.5"H x 11" Ext.	1-13W GU24 Spiral CFL (Incl.)	Title 24
9153-A357-PL	Wall Mount	11"W x 14.25"H x 14.5" Ext.	1-26W GU24 Spiral CFL (Incl.)	Title 24
9154-A357-PL	Chain Hung	11" Dia. x 16.25"H	1-26W GU24 Spiral CFL (Incl.)	Title 24
9156-A357-PL	Post Mount	9" Dia. x 17"H	1-26W GU24 Spiral CFL (Incl.)	Title 24



8763-166-PL



8761-166-PL



8762-166-PL


Finish:  
Corona Bronze™

Glass:  
White Double French Scavo Glass

Features:

- » Cast Aluminum Construction
- » California Title 24 Compliant
- » Compact Fluorescent Bulbs (Incl.)
- » Also available:
  - Black - LED, page 16
  - Corona Bronze™ - Incandescent, page 78
- » See Finish Disclaimer on page 200

Item No.	Type	Size	Watt	Notes
8761-166-PL	Wall Mount	6.25"W x 12.25"H x 7.75" Ext.	1-13W GU24 Spiral CFL (Incl.)	Title 24
8762-166-PL	Wall Mount	8"W x 16.25"H x 9.5" Ext.	1-13W GU24 Spiral CFL (Incl.)	Title 24
8763-166-PL	Wall Mount	10"W x 20"H x 12" Ext.	1-13W GU24 Spiral CFL (Incl.)	Title 24



72002-A138-PL



72001-A138-PL

Finish:  
Aspen Bronze™

Glass:  
Rustic Scavo Glass

Features:

- » Aluminum Construction
- » Closed Top/Open Bottom
- » California Title 24 Compliant
- » Compact Fluorescent Bulbs (Incl.)
- » See Finish Disclaimer on page 200

Item No.	Type	Size	Watt	Notes
72001-A138-PL	Pocket Lantern	9.25"W x 12.75"H x 6" Ext.	1-13W GU24 Spiral CFL (Incl.)	Title 24
72002-A138-PL	Pocket Lantern	9.25"W x 18.5"H x 6" Ext.	2-13W GU24 Spiral CFL (incl.)	Title 24

# Sterling Heights



72353-615B-PL



72352-615B-PL



72356-615B-PL

Finish:  
Dorian Bronze™

Glass:  
Etched Opal Glass

**Features:**

- » Aluminum Construction
- » California Title 24 Compliant
- » Compact Fluorescent Bulbs (Incl.)
- » See Finish Disclaimer on page 200

Item No.	Type	Size	Watt	Notes
72352-615B-PL	Wall Mount	4.5"W x 12.5"H x 5" Ext.	1-13W GU24 Spiral CFL (Incl.)	Title 24
72353-615B-PL	Wall Mount	6"W x 16.25"H x 6.25" Ext.	1-26W GU24 Spiral CFL (Incl.)	Title 24
72356-615B-PL	Post Mount	6"L x 6"W x 17"H	1-26W GU24 Spiral CFL (Incl.)	Title 24



# Skyline



72502-A144-PL



72501-A144-PL



72502-615B-PL



72501-615B-PL



Finish:  
Brushed Aluminum  
Dorian Bronze™

Glass:  
Metal Shade

**Features:**

- » Aluminum Construction
- » California Title 24 Compliant
- » Compact Fluorescent Bulbs (Incl.)
- » Also available:  
Brushed Aluminum Dark-Sky - LED, page 38  
Dorian Bronze™ Dark-Sky - LED, page 38
- » See Finish Disclaimer on page 200

Item No.	Type	Size	Watt	Notes
72501-A144-PL	Wall Mount	5"W x 7.5"H x 6.75" Ext.	1-26W GU24 Spiral CFL (Incl.)	Closed Top/Open Bottom Title 24
72501-615B-PL	Wall Mount	5"W x 7.5"H x 6.75" Ext.	1-26W GU24 Spiral CFL (Incl.)	Closed Top/Open Bottom Title 24
72502-A144-PL	Wall Mount	5"W x 14.5"H x 6.75" Ext.	2-26W GU24 Spiral CFL (Incl.)	Title 24
72502-615B-PL	Wall Mount	5"W x 14.5"H x 6.75" Ext.	2-26W GU24 Spiral CFL (Incl.)	Title 24

# Bay View™



STAINLESS STEEL



9803-144-PL



9803-143-PL

Finish:  
Brushed Stainless Steel  
Oil Rubbed Bronze

Glass:  
Etched Opal Glass

**Features:**

- » Stainless Steel Construction
- » Ideal for areas with harsh weather conditions
- » California Title 24 Compliant
- » Compact Fluorescent Bulbs (Incl.)
- » Also available:
  - Brushed Stainless Steel - LED, page 37
  - Oil Rubbed Bronze - LED, page 37
  - Brushed Stainless Steel - Incandescent, page 122
  - Oil Rubbed Bronze - Incandescent, page 122
- » See Finish Disclaimer on page 200

STAINLESS STEEL

Item No.	Type	Size	Watt	Notes
9801-143-PL	Pocket Lantern	7"W x 9.5"H x 4" Ext.	1-13W GU24 Spiral CFL (Incl.)	Title 24 ADA Compliant
9801-144-PL	Pocket Lantern	7"W x 9.5"H x 4" Ext.	1-13W GU24 Spiral CFL (Incl.)	Title 24 ADA Compliant
9802-143-PL	Pocket Lantern	7.75"W x 12"H x 4.5" Ext.	1-26W GU24 Spiral CFL (Incl.)	Title 24
9802-144-PL	Pocket Lantern	7.75"W x 12"H x 4.5" Ext.	1-26W GU24 Spiral CFL (Incl.)	Title 24
9803-143-PL	Pocket Lantern	8"W x 20.5"H x 4.5" Ext.	2-13W GU24 Spiral CFL (Incl.)	Title 24
9803-144-PL	Pocket Lantern	8"W x 20.5"H x 4.5" Ext.	2-13W GU24 Spiral CFL (Incl.)	Title 24
9806-143-PL	Post Mount	8" Dia. x 12.5" H	1-26W GU24 Spiral CFL (Incl.)	Title 24
9806-144-PL	Post Mount	8" Dia. x 12.5" H	1-26W GU24 Spiral CFL (Incl.)	Title 24

STAINLESS STEEL

Bay View™



9802-144-PL



9802-143-PL



9801-144-PL

STAINLESS STEEL



9806-144-PL



9806-143-PL



9801-143-PL



1490-A357-PL



1492-A357-PL

Finish:  
Iron Oxide

Glass:  
Etched Vanilla Glass

Features:

- » Hand Applied Multi-Step Finish
- » California Title 24 Compliant
- » Indoor/Outdoor
- » Compact Fluorescent Bulbs (Incl.)
- » See Minka-Lavery® catalog for complete section of complementary fixtures and accessories
- » See Finish Disclaimer on page 200

Item No.	Type	Size	Watt	Notes
1490-A357-PL	Pocket Lantern	8"W x 9.75"H x 4" Ext.	1-13W GU24 Spiral CFL (Incl.)	Title 24 ADA Compliant
1492-A357-PL	Pocket Lantern	8"W x 18.5"H x 4" Ext.	2-13W GU24 Spiral CFL (Incl.)	Title 24 ADA Compliant



8201-94-PL



8202-94-PL



8202-61-PL



8206-94-PL



8206-61-PL



8201-61-PL

Finish:  
Heritage™  
Vintage Rust™

Glass:  
One Piece Etched Opal Glass

**Features:**

- » Cast Aluminum Construction
- » Hand Applied Multi-Step Finish
- » California Title 24 Compliant
- » Compact Fluorescent Bulbs (Incl.)
- » Also available:  
Heritage™ - Incandescent, page 140  
Vintage Rust™ - Incandescent, page 140
- » See Finish Disclaimer on page 200

Item No.	Type	Size	Watt	Notes
8201-61-PL	Wall Mount	6.5"W x 14.25"H x 7.5" Ext.	1-13W GU24 Spiral CFL (Incl.)	Title 24 U.S. Patent(s): D510,453; D512,793; D518,224
8201-94-PL	Wall Mount	6.5"W x 14.25"H x 7.5" Ext.	1-13W GU24 Spiral CFL (Incl.)	Title 24 U.S. Patent(s): D510,453; D512,793; D518,224
8202-61-PL	Wall Mount	8.75"W x 17"H x 10.25" Ext.	1-13W GU24 Spiral CFL (Incl.)	Title 24 U.S. Patent(s): D510,453; D512,793; D518,224
8202-94-PL	Wall Mount	8.75"W x 17"H x 10.25" Ext.	1-13W GU24 Spiral CFL (Incl.)	Title 24 U.S. Patent(s): D510,453; D512,793; D518,224
8206-61-PL	Post Mount	8.75" Dia. x 17.25"H	1-13W GU24 Spiral CFL (Incl.)	Title 24 U.S. Patent(s): D510,453
8206-94-PL	Post Mount	8.75" Dia. x 17.25"H	1-13W GU24 Spiral CFL (Incl.)	Title 24 U.S. Patent(s): D510,453

# Cranston™



Finish:  
Heritage™  
Vintage Rust™

Glass:  
One Piece Etched Driftwood Glass

- Features:
- » Cast Aluminum Construction
  - » Hand Applied Multi-Step Finish
  - » California Title 24 Compliant
  - » Compact Fluorescent Bulbs (Incl.)
  - » Closed Bottom
  - » Also available:
    - Vintage Rust™ - Incandescent, page 139
    - Heritage™ - Incandescent, page 139
  - » See Finish Disclaimer on page 200



8252-94-PL



8251-94-PL

Item No.	Type	Size	Watt	Notes
8251-94-PL	Wall Mount	6.5"W x 8.75"H x 8" Ext.	1-13W GU24 Spiral CFL (Incl.)	Title 24
8252-94-PL	Wall Mount	6.5"W x 12.75"H x 10.75" Ext.	1-13W GU24 Spiral CFL (Incl.)	Title 24

# Danbury™



Finish:  
Antique Bronze  
Heritage™

Glass:  
Acid Etched Twist and Lock Glass

- Features:
- » Cast Aluminum Construction
  - » California Title 24 Compliant
  - » Compact Fluorescent Bulbs (Incl.)
  - » See Finish Disclaimer on page 200



71153-94-PL



71153-91-PL

Item No.	Type	Size	Watt	Notes
71153-91-PL	Wall Mount	6"W x 7.25"H x 7.5" Ext.	1-13W GU24 Spiral CFL (Incl.)	Title 24
71153-94-PL	Wall Mount	6"W x 7.25"H x 7.5" Ext.	1-13W GU24 Spiral CFL (Incl.)	Title 24

# Basic CFL



9928-66-PL



9920-44-PL



9920-66-PL

Finish:  
Black  
White

**Features:**

- » Cast Aluminum Construction
- » California Title 24 Compliant
- » Compact Fluorescent Bulbs (Incl.)
- » See Finish Disclaimer on page 200

Item No.	Type	Size	Watt	Notes
9920-44-PL	Pocket Lantern	7.75"W x 9.25"H x 4.5" Ext.	1-13W GU24 Spiral CFL (Incl.)	Title 24
9920-66-PL	Pocket Lantern	7.75"W x 9.25"H x 4.5" Ext.	1-13W GU24 Spiral CFL (Incl.)	Title 24
9928-66-PL	Flush Mount	11.25" Dia. x 5"H	1-13W GU24 Spiral CFL (Incl.)	Title 24

# Flush Mounts



8999-61A



8999-61B



8769-166



9909-1-66



9909-94



8619-A61



71174-66



71174-91



8889-A39



8889-A61



71199-A357-PL



8609-A179-PL



8729-A615B



72029-A179-PL

## FINISHES:

- 39 Spanish Iron™
- 61 Vintage Rust™
- 61A Vintange Rust™
- 61B Green Vintange Rust™
- 66 Black
- 91 Antique Bronze
- 94 Heritage™
- 166 Corona Bronze™
- 179 Textured French Bronze
- 357 Iron Oxide
- 615 Dorian Bronze™

Item No.	Type	Size	Watt	Notes
8609-A179-PL	Flush Mount	9.5"L x 9.5"W x 7"H	1-13W GU24 Spiral CFL (Incl.)	
8619-A61	Flush Mount	16.5" Dia. x 5.75" H	2-40W Candelabra Base	
8729-A615B	Flush Mount	11.25" Dia. x 4.75"H	2-60W Medium Base	
8769-166	Flush Mount	13" Dia. x 7.25"H	2-60W Medium Base	
8889-A39	Flush Mount	12.75" Dia. x 7"H	3-40W Candelabra Base	
8889-A61	Flush Mount	12.75" Dia. x 7"H	3-40W Candelabra Base	
8999-61A	Flush Mount	8.5" Dia. x 12"H	1-60W Candelabra Base	
8999-61B	Flush Mount	8.5" Dia. x 12"H	1-60W Candelabra Base	
9909-1-66	Flush Mount	11.75" Dia. x 8.5"H	2-40W Candelabra Base	
9909-94	Flush Mount	11.75" Dia. x 9.75"H	2-40W Candelabra Base	
71174-66	Flush Mount	10.75" Dia. x 6.75"H	3-40W Candelabra Base	
71174-91	Flush Mount	10.75" Dia. x 6.75"H	3-40W Candelabra Base	
71199-A357-PL	Flush Mount	10"L x 10"W x 7"H	2-13W GU24 Spiral CFL (Incl.)	
72029-A179-PL	Flush Mount	11.5" Dia. x 4.75"H	1-26W GU24 Spiral CFL (Incl.)	



72142-609-PL  
Folio



72141-609-PL  
Folio



9221-256  
Regal Bay



8231-94-PL  
Amarante™



8252-61-PL  
Cranston™



8253-61-PL  
Cranston™



- Finish:
- 94 Heritage™
  - 256 Regal Bay Patina
  - 609 Silver
  - 61 Vintage Rust™

Glass:  
Mouth Blown Clear Hammered Glass  
One Piece Etched Driftwood Glass

Features:  
» Hand Applied Multi-Step Finish  
» See Finish Disclaimer on page 200

Item No.	Type	Size	Watt	Notes
8231-94-PL	Wall Mount	7"W x 10.75"H x 7" Ext.	1-13W GU24 Spiral CFL (Incl.)	
8252-61-PL	Wall Mount	8.5"W x 12.75"H x 10.75" Ext.	1-13W GU24 Spiral CFL (Incl.)	Title 24
8253-61-PL	Wall Mount	10.5"W x 15.75"H x 13" Ext.	1-20W GU24 Spiral CFL (Incl.)	Title 24
9221-256	Wall Mount	5.5"W x 12.5"H x 7.25" Ext.	1-60W Medium Base	
72141-609-PL	Wall Mount	4.75"W x 6.25"H x 5.75" Ext.	1-13W GU24 Spiral CFL (Incl.)	Recessed Light Source Title 24
72142-609-PL	Wall Mount	6.75"W x 9.5"H x 8.25" Ext.	1-26W GU24 Spiral CFL (Incl.)	Recessed Light Source Title 24

# Posts and Mounts



As a complement to our extensive The Great Outdoors® collection, we now offer a selection of pier mounts and posts.



7900-61  
Direct Burial Post  
3"Dia. 96"H  
Additional Finishes  
7900-66  
7900-91  
7900-94  
7900-166  
7900-357



7901-66  
Direct Burial Post  
3"Dia. 102.5"H  
Additional Finishes  
7901-91  
7901-407



7902-66  
Post with Base  
10"Dia. 83.25"H  
Additional Finishes  
7902-61  
7902-94  
7902-198B



Post with Base  
13"Dia. 96"H  
Additional Finishes  
7907-61  
7907-66




7940-94  
Scroll Pier Mount  
12.5"Dia. x 14.25"H  
Additional Finishes  
7940-407

7940-94  
Shown with  
8936-95



7910-66  
Pier Mount  
8.25"Dia. x 9"H



7930-39  
Pier Mount  
5.75"L x 5.75"W x 3.5"H  
Additional Finishes

- |         |          |           |
|---------|----------|-----------|
| 7930-51 | 7930-94  | 7930-199  |
| 7930-57 | 7930-162 | 7930-357  |
| 7930-61 | 7930-163 | 7930-407  |
| 7930-66 | 7930-166 | 7930-615B |
| 7930-91 | 7930-188 |           |

See Finish Disclaimer on page 200

# Finishes

---

## Finish Codes (Alphabetical)

298	Aged Kinston Bronze
246	Alder Bronze
262	Allendale Bronze
163	Amarante Gold™
91	Antique Bronze
171	Architectural Bronze
291	Architectural Bronze with Copper Highlights
138	Aspen Bronze™
184	Aston Patina
66	Black
585	Black with Gold Highlights
A144	Brushed Aluminum
144	Brushed Stainless Steel
51A	Burnt Rust
189	Chelesa Bronze™
166	Corona Bronze™
593	Dark Rubbed Sienna with Aged Silver
277	Dark Sienna Bronze
615B	Dorian Bronze™
212	English Brass
586	Forged Bronze
173	Forged Silver
94	Heritage™
95	Heritage™ with Gold Highlights
357	Iron Oxide
161	Mossoro Walnut™ with Silver Highlights
252	Nanti Champagne Silver
143	Oil Rubbed Bronze
143C	Oil Rubbed Bronze with Gold Highlights
149	Portsmouth Bronze
407	Prussian Gold™
198B	Ravello Bronze™ with Gold Highlights
256	Regal Bay Patina
57	Roman Bronze™
51	Rust
067	Rustic Bronze
609	Silver
39	Spanish Iron™
179	Textured French Bronze
247	Tinted Silver
61	Vintage Rust™
44	White
571	Whisper Bronze
188	Windsor Rust™

# Finish Codes



39  
Spanish Iron™




44  
White



51  
Rust



51A  
Burnt Rust



57  
Roman Bronze™



61  
Vintage Rust™



66  
Black



67  
Rustic Bronze



91  
Antique Bronze



94  
Heritage™




95  
Heritage™  
with Gold Highlights



138  
Aspen Bronze™




143  
Oil Rubbed Bronze



143C  
Oil Rubbed Bronze  
with Gold Highlights



A144  
Brushed Aluminum



144  
Brushed Stainless Steel



149  
Portsmouth Bronze



161  
Mossoro Walnut™  
with Silver Highlights



163  
Amarante Gold™



166  
Corona Bronze™

# Finish Codes



171  
Architectural Bronze



173  
Forged Silver



179  
Textured French Bronze



184  
Aston Patina



188  
Windsor Rust™




189  
Chelesa Bronze™



198B  
Ravello Bronze™  
with Gold Highlights



212  
English Brass



246  
Alder Bronze



247  
Tinted Silver



252  
Nanti Champagne Silver



256  
Regal Bay Patina



262  
Allendale Bronze



277  
Dark Sienna Bronze



291  
Architectural Bronze  
with Copper Highlights



298  
Aged Kinston Bronze



357  
Iron Oxide



407  
Prussian Gold™




609  
Silver



615B  
Dorian Bronze™


Hand-painted finishes and components made from natural materials may reflect variations in color and texture. These are not imperfections and enhance the unique appearance of each and every Minka-Lavery® fixture. Specifications are subject to change at any time.

# Measurement Specifications




## Wall Mounted Lights

Measurements:  
W x H x Ext.




## Ceiling Mount Lights

Measurements:  
Dia. x H



## Ceiling Mount Lights


Measurements:  
L x W x H



Adjustable Stem


## Adjustable Portable Lights

Measurements:  
Dia. x H or L x W x H  
Adjustable to # "L" # "H" Max.



## Adjustable Wall Mounted Lights

Measurements:  
W x H x Ext.  
Adjustable to # "W" # "H" Max.




## Portable Lights


Measurements:  
Dia. x H or L x W x H

## Rod-Drop Lights

Measurements:  
Dia. x H  
Adjustable to # "H" Max.




Adjustable  
Down-Rod and  
Canopy



## Chain Hung Lights

Measurements:  
L x W x H




## Chain Hung Lights


Measurements:  
Dia. x H

## Rod-Drop Lights

Measurements:  
L x W x H  
Adjustable to # "H" Max.




Adjustable  
Down-Rod and  
Canopy



## Post Mount Lights

Measurements:  
Dia. x H



## Post Mount Lights

Measurements:  
L x W x H

# Bulb Chart



**Watts: 10W / 20W**  
XENON JCX 12V  
G4 BI-PIN BASE

Frosted  
JX4-20 (20W)  
Clear  
JX4C-10 (10W)  
JX4C-20 (20W)



**Watts: 35W / 50W**  
XENON JCX 12V  
GY6.35 BI-PIN BASE

Frosted  
JX6-35 (35W)  
JX6-50 (50W)



**Watts: 25W / 35W / 40W / 60W / 75W**  
G9 XENON 120V  
G9 BASE

Frosted  
JX9-025 (25W)  
JX9-035 (35W)  
JX9-040 (40W)  
JX9-060 (60W)  
JX9-075 (75W)  
Clear  
JX9C-025 (25W)  
JX9C-040 (40W)



**Watts: 20W / 50W**  
XENON 120V  
DC (BAYONET)

JXB15-20 (20W)  
JXB15-50 (50W)



**Watts: 75W**  
XENON 120V  
E12 (CANDELABRA) BASE

Frosted  
JDXF-12-075 (75W)



**Watts: 50W / 75W / 100W**  
MINI-CAN XENON 120V  
E11 (CANDELABRA) BASE

Frosted  
JDX-050 (50W)  
JDX-75 (75W)



**Watts: 50W / 75W / 100W**  
MINI-CAN HALOGEN 120V  
E11 (CANDELABRA) BASE

Frosted  
JDC-50 (50W)  
JDC-75 (75W)  
JDC-100 (100W)  
Clear  
JD-50 (50W)  
JD-75 (75W)  
JD-100 (100W)



**Watts: 50W**  
JDD XENON 120V  
E12 (CANDELABRA) BASE

Frosted  
JDX2F-050 (50W)  
Clear  
JDX2-050 (50W)



**Watts: 100W / 150W**  
78MM 120V DOUBLE ENDED  
HALOGEN (J-TYPE)  
R7S BASE

JB-100 (100W)  
JB-150 (150W)



**Watts: 8W DC / 10W AC / 11W AC / 14W AC**  
LED MODULE

L-L8-MD590 (8W)  
L-AC10-MODULE (10W)  
L-AC10-MD770 (11W)  
L-AC14-MD950 (14W)



**Watts: 50W**  
PAR16 HALOGEN  
E26 (MEDIUM) BASE

PAR16-50 (50W)



**Watts: 35W / 50W**  
HALOGEN MR16 120V  
GU10 BASE

JGU-035 (35W)  
JGU-50 (50W)



**Watts: 20W / 35W / 50W**  
HALOGEN MR16  
GX5.3 BI-PIN BASE

Frosted  
JMR16-20 (20W 120V)  
JMR16-35 (35W 120V)  
JMR16-50/120V (50W 120V)  
Clear  
JMR16-C-20 (20W 12V)  
JMR16-C-35 (35W 12V)  
JMR16-C-50 (50W 12V)



**Watts: 13W / 26W**  
SPIRAL CFL  
E26 (MEDIUM) BASE

FLB-13S (13W)



**Watts: 13W / 26W**  
SPIRAL CFL  
GU24 BASE

FLB-13M (13W)  
FLB-26M (26W)




**Watts: 18W / 26W**  
SQUAT SPIRAL CFL  
GU24 BASE

FLS-18M (18W)  
FLS-26M (26W)



**Watts: 40W**  
FERRO  
E26 (MEDIUM) BASE

E26-FW1910-40W (40W)



**Watts: 40W / 60W / 100W**  
T10 120V  
E26 (MEDIUM) BASE

Frosted  
JT10-060F (60W)  
Clear  
JT10-040C (40W)  
JT10-060C (60W)  
JT10-100C (100W)



**Watts: 27W**  
FULL 24 CFL  
GX10q-4 BASE

JT4-27 (27W)




**Watts: 13W**  
4-PIN (PL-C)  
G24q-1 BASE

FLT-13Q (13W)



**Watts: 27W**  
CFL  
GX10q-4 BASE

JT2-27 (27W)



**Watts: 32W**  
FC12T9 T9 CIRCULINE  
G10Q

FLC-22 (22W)  
FLC-32 (32W)  
FLC-40 (40W)



**Watts: 8W / 13W**  
FLUORESCENT  
T5 G13 BI-PIN BASE

Ballast: BLST08-T5  
JT5-8  
JT5-13



**Watts: 7W**  
C7 CFL  
E12 (CANDELABRA) BASE

FLB-07C (7W)



**Watts: 75W**  
MR16  
E17 BASE

JDR-75 (75W)



**Watts: 40W / 60W**  
B10.5  
E12 (CANDELABRA) BASE

E12 (CANDELABRA) BASE



**Watts: 15W**  
C7  
E12 (CANDELABRA) BASE

ECCC-15 (15W)



**Watts: 60W**  
BR30  
E26 (MEDIUM) BASE



**Watts: 40W / 60W**  
A15  
E26 (MEDIUM) BASE



**Watts: 40W / 60W / 75W / 100W**  
A19  
E26 (MEDIUM) BASE



**Watts: 150W**  
A21 (3-WAY)  
E26 (MEDIUM) BASE



**Watts: 25W / 40W / 60W**  
G16 1/2  
E12 (CANDELABRA) BASE



**Watts: 60W / 100W**  
G25  
E26 (MEDIUM) BASE



**Watts: 60W / 100W**  
G30  
E26 (MEDIUM) BASE



**Watts: 40W / 60W / 100W**  
G40  
E26 (MEDIUM) BASE

# Index

Model No.	Page	Model No.	Page	Model No.	Page
1245-246-L	34	7940-407	184	8251-94	139
1246-246-L	34	8101-A138	144	8251-94-PL	180
1490-A357-PL	178	8101-A138-L	13	8252-61	139
1492-A357-PL	178	8102-A138	144	8252-61-PL	183
7900-61	184	8102-A138-L	13	8252-94	139
7900-66	184	8106-A138	144	8252-94-PL	180
7900-91	184	8106-A138-L	13	8253-61-PL	183
7900-94	184	8121-A188-PL	146	8256-61	139
7900-166	184	8122-A188-PL	146	8256-94	139
7900-357	184	8126-A188-PL	146	8261-66-L	26
7901-66	184	8131-173-L	14	8261-161	89
7901-91	184	8132-173-L	15	8262-66-L	27
7901-407	184	8134-173-L	14	8262-161	88
7902-61	184	8136-173-L	14	8263-66-L	26
7902-66	184	8151-568-L	36	8263-161	88
7902-94	184	8152-568-L	36	8264-66-L	27
7902-198B	184	8153-568-L	36	8264-161	89
7907-61	184	8154-568-L	36	8265-66-L	27
7907-66	184	8161-615B-L	30	8265-161	88
7910-66	184	8162-615B-L	31	8266-66-L	27
7930-39	184	8164-615B-L	30	8266-161	88
7930-51	184	8166-615B-L	30	8267-66-L	26
7930-57	184	8201-61	140	8267-161	89
7930-61	184	8201-61-PL	179	8268-161	88
7930-66	184	8201-94	140	8271-A357-L	29
7930-91	184	8201-94-PL	179	8272-A357-L	29
7930-94	184	8202-61	140	8273-A357-L	28
7930-162	184	8202-61-PL	179	8274-A357-L	29
7930-163	184	8202-94	140	8276-A357-L	29
7930-166	184	8202-94-PL	179	8281-A61	143
7930-188	184	8206-61	140	8282-A61	143
7930-199	184	8206-61-PL	179	8283-A61	143
7930-357	184	8206-94	140	8284-A61	143
7930-407	184	8206-94-PL	179	8286-A61	143
7930-615B	184	8231-94-PL	183	8560-51	113
7940-94	184	8251-61	139	8561-51	113



Model No.	Page	Model No.	Page	Model No.	Page
8562-51	113	8697-1-61-PL	165	8816-57	76
8563-51	113	8697-61	63	8817-57	76
8567-51	113	8697-66	59	8840-94	75
8581-51	112	8698-1-61-PL	164	8841-94	75
8582-51	112	8698-61	63	8842-94	74
8601-A179-PL	155	8698-66	60	8844-94	75
8602-A179-PL	155	8717-66	138	8845-94	75
8603-A179-PL	155	8717-91	138	8846-94	75
8605-A179-PL	155	8718-66	138	8847-94	74
8609-A179-PL	155,182	8718-91	138	8880-A39	108
8611-A61	81	8721-A615B	137	8880-A39-PL	167
8612-A61	80	8722-A615B	137	8880-A61	110
8613-A61	80	8723-A615B	136	8881-A39	106
8614-A61	80	8724-A615B	137	8881-A39-PL	167
8616-A61	80	8725-A615B	137	8881-A61	110
8617-A61	81	8726-A615B	137	8882-A39	107
8619-A61	80,182	8729-A615B	136,182	8882-A39-PL	166
8690-1-61-PL	164	8761-66-L	17	8882-A61	111
8690-61	63	8761-166	78	8883-A39	105
8690-66	60	8761-166-PL	172	8883-A61	109
8691-1-61-PL	164	8762-66-L	17	8884-A39	106
8691-61	62	8762-166	79	8884-A61	111
8691-66	59	8762-166-PL	172	8885-A39	108
8692-1-61-PL	165	8763-66-L	16	8885-A39-PL	167
8692-61	62	8763-166	78	8885-A61	111
8692-66	59	8763-166-PL	172	8886-A39	107
8693-61	61	8764-66-L	17	8887-A39	107
8693-66	58	8764-166	79	8887-A39-PL	167
8694-61	62	8765-166	79	8887-A61	110
8694-66	60	8766-66-L	17	8889-A39	108,182
8695-1-61-PL	164	8766-166	79	8889-A61	110,182
8695-61	63	8769-166	79,182	8900-94	72
8695-66	60	8810-57	76	8901-94	71
8696-1-61-PL	164	8811-57	76	8902-94	70
8696-61	62	8812-57	77	8903-94	69
8696-66	59	8815-57	76	8904-94	71

# Index

Model No.	Page	Model No.	Page	Model No.	Page
8905-94	73	9060-66	141	9251-A199-PL	158
8906-94	73	9060-91	141	9252-A199-PL	158
8907-94	70	9066-66	141	9253-A199-PL	159
8908-94	72	9067-66	141	9256-A199-PL	158
8909-94	73	9067-91	141	9281-171	100
8930-95	56	9071-264	50	9282-171	100
8931-95	57	9072-264	50	9283-171	101
8932-95	56	9073-264	51	9286-171	100
8933-95	55	9091-95	54	9311-586	46
8934-95	55	9094-95	57	9312-586	44
8935-95	55	9141-407	83	9313-586	45
8936-95	56,184	9141-407-PL	163	9314-586	46
8937-95	57	9142-407	82	9316-586	44
8990-61	68	9142-407-PL	163	9321-585	42
8990-61-PL	161	9143-407	82	9322-585	43
8990-66	64	9143-407-PL	162	9323-585	41
8991-61	67	9144-407	82	9324-585	42
8991-61-PL	161	9146-407	82	9326-585	43
8991-66	64	9146-407-PL	163	9801-143	123
8992-61	66	9147-407	83	9801-143-L	37
8992-61-PL	160	9151-A357	134	9801-143-PL	177
8992-66	65	9151-A357-PL	170	9801-144	123
8994-61	67	9152-A357	134	9801-144-L	37
8995-61	68	9152-A357-PL	170	9801-144-PL	177
8995-61-PL	161	9153-A357	135	9802-143	123
8995-66	64	9153-A357-PL	171	9802-143-L	37
8996-61	68	9154-A357	134	9802-143-PL	177
8997-61	67	9154-A357-PL	170	9802-144	123
8997-61-PL	161	9156-A357	134	9802-144-L	37
8997-66	64	9156-A357-PL	170	9802-144-PL	177
8999-61A	182	9190-189-PL	169	9803-143	122
8999-61B	182	9192-189-PL	169	9803-143-PL	176
9010-66	84	9193-189-PL	168	9803-144	122
9011-66	84	9194-189-PL	169	9803-144-PL	176
9016-66	84	9195-189-PL	169	9806-143	123
9018-66	84	9221-256	183	9806-143-PL	177

Model No.	Page	Model No.	Page	Model No.	Page
9806-144	123	71824-143-L	19	72212-615B	145
9806-144-PL	177	71826-143-L	19	72212-A144	145
9811-166	124	72001-A138-PL	173	72221-571-L	32
9812-166	124	72002-A138-PL	173	72222-571-L	32
9813-166	124	72011-A173-PL	154	72231-143C	121
9836	147	72012-A173-PL	154	72232-143C	121
9838	147	72016-A173-PL	154	72233-143C	120
9909-1-66	65,182	72020-A179-PL	156	72234-143C	120
9909-94	73,74,182	72021-A179-PL	156	72236-143C	121
9920-44-PL	181	72022-A179-PL	156	72251-66	149
9920-66-PL	181	72023-A179-PL	157	72252-66	149
9928-66-PL	181	72026-A179-PL	156	72253-66	149
71153-91-PL	180	72029-A179-PL	156,182	72261-189	117
71153-94-PL	180	72111-149	102	72262-189	117
71163-143C	116	72112-149	102	72291-291	104
71163-143C-L	12	72113-149	103	72292-291	104
71163-A144	116	72114-149	102	72294-291	104
71163-A144-L	11	72116-149	102	72301-291	94
71166-91	117	72121-144-PL	125	72302-291	94
71167-91	117	72122-144-PL	125	72303-291	95
71169-143C-L	12	72141-609-PL	183	72306-291	94
71169-A144-L	11	72142-609-PL	183	72311-615B	130
71174-66	182	72161-179	118	72312-615B	130
71174-91	182	72162-179	119	72313-615B	130
71190-A357-PL	153	72164-179	118	72321-247	148
71191-A357-PL	153	72166-179	118	72322-247	148
71192-A357-PL	153	72170-189	87	72331-291	131
71193-A357-PL	151	72171-189	86	72332-291	131
71194-A357-PL	152	72172-189	87	72336-291	131
71195-A357-PL	153	72173-189	86	72342-615B	129
71196-A357-PL	152	72174-189	87	72343-615B	129
71197-A357-PL	152	72176-189	87	72352-615B-PL	174
71198-A357-PL	152	72191-144	125	72353-615B-PL	174
71199-A357-PL	153,182	72192-144	125	72356-615B-PL	174
71821-143-L	19	72211-615B	145	72371-615B	128
71822-143-L	18	72211-A144	145	72372-615B	128

# Index

Model No.	Page	Model No.	Page	Model No.	Page
72381-246	127	72501-A144-PL	175	73094-189	115
72382-246	127	72502-615B-L	38	73096-189	115
72383-246	126	72502-615B-PL	175	73101-143C-L	20
72391-143C	24	72502-A144-L	38	73102-143C-L	20
72392-143C	24	72502-A144-PL	175	73103-143C-L	21
72393-143C	24	72511-246	98	73106-143C-L	20
72396-143C	24	72512-246	98		
72397-143C	25	72513-246	99		
72399-615B-L	35	72514-246	98		
72400-615B	147	72516-246	98		
72400-615B-L	35	72521-246	90		
72401-287B-L	33	72522-246	90		
72402-287B-L	33	72523-246	91		
72411-51A-L	23	72524-246	90		
72412-51A-L	23	72526-246	90		
72413-51A-L	22	72531-143	92		
72414-51A-L	23	72532-143	92		
72416-51A-L	23	72533-143	93		
72420-212	49	72534-143	92		
72421-212	48	72536-143	92		
72422-212	49	72540-593-L	96		
72423-212	48	72541-593	97		
72424-212	49	72542-593	96		
72425-212	48	72543-593	97		
72426-212	49	72544-593	96		
72427-212	47	72546-593	96		
72431-261	52	73001-143C	85		
72432-261	52	73003-143C	85		
72433-261	53	73061-246	133		
72434-261	52	73062-246	133		
72436-261	52	73063-246	132		
72440-291-L	39	73064-246	133		
72441-291-L	39	73066-246	133		
72501-615B-L	38	73091-189	115		
72501-615B-PL	175	73092-189	115		
72501-A144-L	38	73093-189	114		



# Notes

---

Blank lined area for notes.

Lined area for taking notes.







# Acknowledgements / Disclaimer / Warranty

---

- Minka-Lavery® will warranty only product sold through authorized Minka-Lavery® dealers.
- All products depicted in this catalog, when properly installed, are UL or ETL listed, suitable for Wet Location. The only exception are flush mounts and chain hung which are UL or ETL listed, suitable for Damp Location.
- We strive to make sure each finish matches the colors which appear in this catalog; however, finishes may vary due to various chemical processes and the nature of hand-craftsmanship.
- Seeded glass (both flat panel and mouth blown) is handmade and variations will occur.
- Larger size lanterns may require reinforced outlet boxes or additional support.
- Although we use the best available clear weather resistant lacquer, we cannot guarantee our exterior finishes due to extreme adverse conditions such as acid rain, ultraviolet rays, salt air, etc.
- We cannot guarantee our direct burial post due to environmental characteristics including moisture, salinity, corrosiveness and other soil and air conditions.
- The finish on our wrought iron series may be affected by direct salt water spray exposure.
- We reserve the right to make design changes and modifications without prior notification.

**WARRANTY** - All products in this catalog, other than our LED fixtures which has a limited Power Supply warranty (Module, PC Board Diodes and Drivers) for three (3) years, are warranted to be free of defects in material and workmanship for one (1) year from date of purchase. This warranty is limited to the correction of any such defect, or the replacement of any such defective item, provided that: (a) item(s) was (were) purchased from an authorized Minka Group® distributor; (b) we are properly notified and consent to the return of the item(s) in question; (c) the item(s) is/are returned with proof of purchase date; and (d) it is found upon inspection by us that the item(s) is/are defective as noted above. This warranty does not cover labor costs or consequential damages, nor does it apply to any item(s) that has/have been improperly installed, overloaded, altered, or otherwise abused by the customer, its agent(s) or employee(s).

All finishes, other than our Ever-Pro™ Series Outdoor product finishes which has a limited warranty for three (3) years, are specifically excluded from the terms of this warranty since they are subject to environmental and maintenance damages beyond our control. Other than the described obligation, we assume no further liability with respect to the sale or use of our products. We make no warranty, express or implied, and disclaim any warranty of merchantability or fitness for a particular purpose.

Product specifications are subject to change at any time.

**GENERAL CONDITIONS** - The Great Outdoors® by Minka-Lavery® may terminate its business relationship with any dealer that fails to maintain adequate stock of The Great Outdoors® product. Further, The Great Outdoors® by Minka-Lavery® may cease selling product to any dealer that sells or distributes to an unauthorized dealer for resale purposes. Trans-shipment of products is prohibited to any and all lighting showrooms or other unspecified distribution channel.

We Support





the**greatoutdoors**<sup>®</sup>  
by MINKA-LAVERY<sup>®</sup>

**World Headquarters**

1151 West Bradford Court, Corona, California 92882

**Showroom**

Dallas Market Center

2100 Stemmons, Suite 3783, Dallas, Texas 75207

800.221.7977 Tel. 951.735.9220 Fax. 951.735.9758

sales@minkagroup.net www.minkagroup.net

\$15.00