

A close-up, low-angle shot of a wooden ceiling fan blade. The blade is made of a dark-stained wood with a prominent vertical grain. It is attached to a dark, cylindrical motor housing. Below the blade, a portion of a white, circular light fixture is visible, emitting a soft glow. The background is a solid, muted brown color.

# CEILING FANS

JANUARY 2015 SUPPLEMENT

*Style to live by™*

**KICHLER®**





54" Porters Lake™  
310110 MDW  
See pages 268-269  
in Catalog No. K414

# NEW FOR 2015 CEILING FANS

## The Kichler® Brand Promise

Since 1938, our family-owned company has created products that blend style with purpose, and our ceiling fans deliver this same attention to detail:

- In-house design, engineering and quality-control assures a superior ceiling fan
- Premium construction you can see and feel in every detail – from solid, durable housings to sturdy, expertly designed blades
- The widest selection of fan styles – from our statement-making décor™ series to the timeless looks of our select™ series to our variety of outdoor options

## More than just a pretty face

Show-stopping styles and flawless finishes are just the start of what you'll love about Kichler Ceiling Fans. We're continuously updating our line to include more on-trend styles, features and finish choices. We've also built in function that's designed to perform: premium motors, superior controls and energy-saving features.

You'll soon discover that your Kichler Ceiling Fan is that one appliance that makes your room both more comfortable and more beautiful.

## Giving you more reasons to love your fan:

For 2015, we're adding select styles and finishes to our collection. Within this catalog supplement, you'll find:

- Fans with a tropical twist, including styles with whitewashed or paneled blades
- New Industrial looks featuring exposed piping, oversized grommets and caged lighting
- New outdoor options that let you bring comfort and style to patios, porches and more



Ask your Kichler® dealer to see our full line catalog, featuring dozens of additional styles, or visit us online at [Kichler.com](http://Kichler.com).



Become a fan of Kichler Lighting at:  
[facebook.com  
search Kichler Lighting](https://www.facebook.com/search/Kichler%20Lighting)



Follow us on  
[twitter.com/kichlerlight](https://twitter.com/kichlerlight)



Watch us on  
[youtube.com/KichlerLighting](https://www.youtube.com/KichlerLighting)

# Fan Visual Index

DÉCOR™



52" CLAYTON  
300195 pg s346



60" HATTERAS BAY™ PATIO  
310117 p s336



65" MAOR™ PATIO  
310136 p s334



52" SHURIKEN™  
300209 pg s338



52" SUNBURST  
300170 pg s342



42" SUNBURST II  
300169 pg s344



15" TERNA™ LED  
300230 pg s340



SELECT™



52" EADS™  
310135 p s350



60" ENTHRALL  
300192 pg s360



52" FRYST™  
300185 pg s352



52" KLEVER  
300199 pg s354



52" ORRIN  
300191 pg s362



60" TULLE™  
300188 pg s356



52" FRYST™ PATIO  
310128 pg s368



60" HATTERAS BAY™ PATIO  
310117 pg s370



52" RENEW™ SELECT PATIO  
339516 pg s374



60" TULLE™ PATIO  
310193 pg s372



ACCESSORIES

## ACCESSORIES

pg s378 – s386

## NUMERIC INDEX

pg s387



15" Terna™ LED  
300230 NI  
See pages s340-s341

## LED LIGHT KIT FANS

- LED lighting can use 50-90% less energy than traditional light sources
- Long life of LED's can be up to 4-5 times longer than traditional light sources
- Generates less heat
- Containing no toxic chemicals LED's are more environmentally friendly than traditional incandescent and fluorescent lamps

LED  
LIGHT KIT





# DÉCOR

---

## CEILING FANS

**Premium crafted designs bring highly traditional, sleek contemporary or soft transitional style to your home**

- Statement-making designs that help you add a dramatic centerpiece to a room
- Decorator-inspired finishes
- Coordinating Kichler Lighting fixtures
- Limited Lifetime Warranty

OUTDOOR  
INDOOR



**310136 DBK**

Finish: Distressed Black  
Glass: Etched Cased Opal  
Blades: Distressed Black



**310136 OZ**

Finish: Olde Bronze®  
Glass: Etched Cased Opal  
Blades: Olde Bronze®



**310136 WZC**

Finish: Weathered Zinc  
Glass: Etched Cased Opal  
Blades: Weathered Zinc





**OPTIONAL CONTROLS**



370039MUL

337214

**COOLTOUCH™ CONTROL SYSTEM – BASIC**

See page 320 in our main catalog for more information  
NOTE: Receiver is wet rated.







**INCLUDED CONTROL**



**PULL CHAIN**

- ★ 3 Forward Speeds
- ★ Manual Reverse

**BLADE SPECS**

Fan Finish	Blade Finish	Part No.
 <p><b>DBK</b> Distressed Black</p>	 <p>Distressed Black</p>	<p>FB310136DBK</p>
 <p><b>OZ</b> Olde Bronze®</p>	 <p>Olde Bronze®</p>	<p>FB310136OZ</p>
 <p><b>WZC</b> Weathered Zinc</p>	 <p>Weathered Zinc</p>	<p>FB310136WZC</p>

**INCLUDED**

- ★ **BLADES** (4) Included ★ 13° Pitch ★ 65" Sweep Non-Reversible ★ Aluminum
- ★ **DOWNRODS** 4.5" Downrod with 1" (O.D.)
- ★ **DOWNLIGHT** Integrated. 17W LED Platform 1,300 Lumens, 80 CRI, 3,000K CCT
- ★ **DOWNLIGHT GLASS** Etched Cased Opal
- ★ **OPTIONAL DOWNLIGHT** N/A
- ★ **UPLIGHT** N/A ★ **UPLIGHT GLASS** N/A
- ★ **LOW CEILING ADAPTABLE** No


**FAN SPECS**

- ★ **MOUNTING SLOPE – PITCH** 30° or 7/12
- ★ **LEAD WIRE** 78" ★ **cETLus LISTED** Damp
- ★ **HANGING WEIGHT** 38.58 lbs.
- ★ **WARRANTY** Limited Lifetime

**MOTOR SPECS**

- ★ **MOTOR SIZE/ TYPE** 212mm x 20mm, AC
- ★ **AMPS** 0.72 ★ **RPM** 137 on High
- ★ **ENERGY STAR** N/A

**HANGING MEASUREMENTS**



WITH 4.5" DOWNROD  
A - 17.60" B - 12.00" C - 13.00"

AIRFLOW	POWER USAGE	AIRFLOW EFFICIENCY
8803 Cubic Ft. Per Minute on High	86 Watts on High (Excludes Lights)	103 Cubic Ft. Per Minute Per Watt

OUTDOOR  
INDOOR



**310117 TZP**  
Finish: Tannery Bronze™ Powder Coat  
Glass: Fresnel Lens  
Blades: Light Walnut

60"  
HATTERAS  
BAY™  
PATIO



**310117 WCP**  
Finish: Weathered Copper™ Powder Coat  
Glass: Fresnel Lens  
Blades: Medium Walnut



**310117 WZC**  
Finish: Weathered Zinc  
Glass: Fresnel Lens  
Blades: Dark Walnut



**310117 DBK**  
Finish: Distressed Black  
Glass: Fresnel Lens  
Blades: Cherry





**OPTIONAL CONTROLS**



TR310117DBK  
TR310117TZP  
TR310117WCP  
TR310117WZC

**3-SPEED COOLTOUCH™ FULL FUNCTION TRANSMITTER**

NOTE: Receiver is Wet Rated. Transmitter for Indoor Use.

**INCLUDED CONTROL**



**WALL CONTROL SYSTEM – FULL FUNCTION**

- ★ 3 Forward Speeds and Reverse
- ★ Light On/Off with Full Range Dimming
- ★ Motor Off
- ★ Receiver Included



**BLADE SPECS**

Fan Finish	Blade Finish	Part No.
<p><b>DBK</b> Distressed Black</p>	Cherry	FB310117DBK
	Light Walnut	FB310117DBK
<p><b>TZP</b> Tannery Bronze™ Powder Coat</p>	Cherry	FB310117TZP
	Light Walnut	FB310117TZP
<p><b>WCP</b> Weathered Copper™ Powder Coat</p>	Dark Walnut	FB310117WCP
	Medium Walnut	FB310117WCP
<p><b>WZC</b> Weathered Zinc</p>	Dark Walnut	FB310117WZC
	Medium Walnut	FB310117WZC

**INCLUDED**

- ★ **BLADES (5)** Included ★ 12° Pitch ★ 60" Sweep Reversible ★ ABS
- ★ **DOWNRODS** 6" Downrod with 1" (O.D.)
- ★ **DOWNLIGHT** Yes. Integrated. Uses (4) E-12 40W B-10.5
- ★ **DOWNLIGHT GLASS** Fresnel Lens
- ★ **OPTIONAL DOWNLIGHT** N/A
- ★ **UPLIGHT** N/A ★ **UPLIGHT GLASS** N/A
- ★ **LOW CEILING ADAPTABLE** Yes, Flush Mount Canopy Included.


**FAN SPECS**

- ★ **MOUNTING SLOPE – PITCH** 22° or 4/12
- ★ **LEAD WIRE** 78" ★ **cUL LISTED** Damp
- ★ **HANGING WEIGHT** 32.36 lbs.
- ★ **WARRANTY** Limited Lifetime

**MOTOR SPECS**

- ★ **MOTOR SIZE/ TYPE** 188mm x 25mm, AC
- ★ **AMPS** 0.57 ★ **RPM** 150 on High
- ★ **ENERGY STAR** N/A

**HANGING MEASUREMENTS**



WITH 6" DOWNROD  
A - 17.52" B - 12.90" C - 15.36"

<p><b>AIRFLOW</b></p> <p>6665 Cubic Ft. Per Minute on High</p>	<p><b>POWER USAGE</b></p> <p>69 Watts on High (Excludes Lights)</p>	<p><b>AIRFLOW EFFICIENCY</b></p> <p>97 Cubic Ft. Per Minute Per Watt</p>
--------------------------------------------------------------------	-------------------------------------------------------------------------	------------------------------------------------------------------------------



**300209 OBB**  
Finish: Oil Brushed Bronze™  
Glass: Etched Cased Opal  
Blades: Walnut Shadowed

52"  
SHURIKEN™



**300209 SBK**  
Finish: Satin Black  
Glass: Etched Cased Opal  
Blades: Dark Driftwood




**300209 NI**  
Finish: Brushed Nickel  
Glass: Etched Cased Opal  
Blades: Driftwood





**OPTIONAL CONTROLS**



**WALL TRANSMITTER – FULL FUNCTION**

See page 321 in our main catalog for more information

**INCLUDED CONTROL**



**3-SPEED COOLTOUCH™ FULL FUNCTION**

- ★ 3 Forward Speeds & Reverse
- ★ Lights On/Off with Full Range Dimming
- ★ Motor Off

**BLADE SPECS**

Fan Finish	Blade Finish	Part No.
<b>NI</b> Brushed Nickel	Driftwood	FB300209NI
<b>OBB</b> Oil Brushed Bronze™	Walnut Shadowed	FB300209OBB
<b>SBK</b> Satin Black	Dark Driftwood	FB300209SBK

**INCLUDED**

- ★ **BLADES (4)** Included ★ 13° Pitch ★ 52" Sweep Non-Reversible ★ ABS
- ★ **DOWNRODS** 4.5" Downrod with 1" (O.D.)
- ★ **DOWNLIGHT** Integrated. 17W Dimmable LED Platform 1,300 Lumens, 80 CRI, 3,000K CCT
- ★ **DOWNLIGHT GLASS** Etched Cased Opal
- ★ **OPTIONAL DOWNLIGHT** N/A
- ★ **UPLIGHT** N/A ★ **UPLIGHT GLASS** N/A
- ★ **LOW CEILING ADAPTABLE** No


**FAN SPECS**

- ★ **MOUNTING SLOPE – PITCH** 30° or 7/12
- ★ **LEAD WIRE** 78" ★ **cETLus LISTED** Indoor
- ★ **HANGING WEIGHT** 22.04 lbs.
- ★ **WARRANTY** Limited Lifetime

**MOTOR SPECS**

- ★ **MOTOR SIZE/ TYPE** 172mm x 17mm, AC
- ★ **AMPS** 0.64 ★ **RPM** 128 on High
- ★ **ENERGY STAR** N/A

**HANGING MEASUREMENTS**



WITH 4.5" DOWNROD  
A - 15.04" B - 8.66" C - 11.77"

<b>AIRFLOW</b> 4750 Cubic Ft. Per Minute on High	<b>POWER USAGE</b> 77 Watts on High (Excludes Lights)	<b>AIRFLOW EFFICIENCY</b> 62 Cubic Ft. Per Minute Per Watt
--------------------------------------------------------	-------------------------------------------------------------	------------------------------------------------------------------

15"

TERNA™  
LED



**300230 NI**

Finish: Brushed Nickel  
Glass: Etched Cased Opal  
Blades: Champagne



**300230 WH**

Finish: White  
Glass: Etched Cased Opal  
Blades: White



**300230 OBB**

Finish: Oil Brushed Bronze™  
Glass: Etched Cased Opal  
Blades: Oil Brushed Bronze™





**OPTIONAL CONTROLS**



**WALL TRANSMITTER – FULL FUNCTION**

See page 321 in our main catalog for more information

**INCLUDED CONTROL**



**3-SPEED COOLTOUCH™ FULL FUNCTION**

- ★ 3 Forward Speeds & Reverse
- ★ Lights On/Off with Full Range Dimming
- ★ Motor Off

**INCLUDED**

- ★ **BLADES** (5) Included ★ Variable ★ 15" Sweep Non-Reversible ★ Polycarbonate
- ★ **DOWNRODS** 4.5" Downrod with 1" (O.D.)
- ★ **DOWNLIGHT** Integrated. 17W Dimmable LED Platform 1,300 Lumens, 80 CRI, 3,000K CCT
- ★ **DOWNLIGHT GLASS** Etched Cased Opal
- ★ **OPTIONAL DOWNLIGHT** N/A
- ★ **UPLIGHT** N/A ★ **UPLIGHT GLASS** N/A
- ★ **LOW CEILING ADAPTABLE** No


**FAN SPECS**

- ★ **MOUNTING SLOPE – PITCH** 30° or 7/12
- ★ **LEAD WIRE** 78" ★ **cUL LISTED** Indoor
- ★ **HANGING WEIGHT** 15.87
- ★ **WARRANTY** Limited Lifetime

**MOTOR SPECS**

- ★ **MOTOR SIZE/ TYPE** 153mm x 15mm, AC
- ★ **AMPS** .28 ★ **RPM** 315 on High
- ★ **ENERGY STAR** N/A

**HANGING MEASUREMENTS**



WITH 4.5" DOWNROD  
A - 19.86" B - 19.13" C - 10.55"

**BLADE SPECS**

Fan Finish	Blade Finish	Part No.
<b>NI</b> Brushed Nickel	Champagne	FB300230NI
<b>OBB</b> Oil Brushed Bronze™	Oil Brushed Bronze	FB300230OBB
<b>WH</b> White	White	FB300230WH

**RETRO-FIT KIT**

LED Retro-Fit kit available to upgrade **300215 Terna™** halogen light kit to an LED light kit.

- 380215 NI**
- 380215 OBB**
- 380215 WH**



**300170 BSS**

Finish: Brushed Stainless Steel  
Glass: Etched Cased Opal  
Blades: Champagne



52"  
SUNBURST



**300170 OBB**

Finish: Oil Brushed Bronze™  
Glass: Etched Cased Opal  
(shown with included metal cap)  
Blades: Oiled Brushed Bronze™



**300170 WH**

Finish: White  
Glass: Etched Cased Opal  
Blades: White



**OPTIONAL CONTROLS**



**337214TR**  
**COOLTOUCH™ TRANSMITTER – BASIC**

See page 321 in our main catalog for more information

**INCLUDED CONTROL**



**WALL CONTROL SYSTEM – BASIC**

- ★ 3 Forward Speeds and Motor Off
- ★ Manual Reverse
- ★ Light On/Off with Full Range Dimming



**INCLUDED**

- ★ **BLADES** (4) Included ★ 14° Pitch ★ 52" Sweep Non-Reversible ★ Polycarbonate
- ★ **DOWNRODS** 4" Downrod with 1" (O.D.)
- ★ **DOWNLIGHT** Integrated. 17W Dimmable LED Platform 1,300 Lumens, 80 CRI, 3,000K CCT
- ★ **DOWNLIGHT GLASS** Etched Cased Opal
- ★ **OPTIONAL DOWNLIGHT** N/A
- ★ **UPLIGHT** N/A ★ **UPLIGHT GLASS** N/A
- ★ **LOW CEILING ADAPTABLE** No


**FAN SPECS**

- ★ **MOUNTING SLOPE – PITCH** 30° or 7/12
- ★ **LEAD WIRE** 78" ★ **cETLus LISTED** Indoor
- ★ **HANGING WEIGHT** 22.75 lbs.
- ★ **WARRANTY** Limited Lifetime

**MOTOR SPECS**

- ★ **MOTOR SIZE/ TYPE** 172mm x 17mm, AC
- ★ **AMPS** 0.58 ★ **RPM** 180 on High
- ★ **ENERGY STAR** N/A

**HANGING MEASUREMENTS**



WITH 4" DOWNROD  
**A - 14.88" B - 10.02" C - 10.63"**

**BLADE SPECS**

Fan Finish	Blade Finish	Part No.
<b>BSS</b> Brushed Stainless Steel	Champagne	FB300170BSS
<b>OBB</b> Oil Brushed Bronze™	Oil Brushed Bronze™	FB300170OBB
<b>WH</b> White	White	FB300170WH

**METAL CAPS**

Includes a metal fixture cap for non-light use



<b>AIRFLOW</b> 6546 Cubic Ft. Per Minute on High	<b>POWER USAGE</b> 70 Watts on High (Excludes Lights)	<b>AIRFLOW EFFICIENCY</b> 94 Cubic Ft. Per Minute Per Watt
--------------------------------------------------------	-------------------------------------------------------------	------------------------------------------------------------------





**300169 OBB**

Finish: Oil Brushed Bronze™  
Glass: Etched Cased Opal  
Blades: Oil Brushed Bronze™

**42"**  
**SUNBURST II**



**300169 WH**

Finish: White  
Glass: Etched Cased Opal  
Blades: White



**300169 BSS**

Finish: Brushed Stainless Steel  
Glass: Etched Cased Opal  
(shown with included metal cap)  
Blades: Champagne



**OPTIONAL CONTROLS**



**337214TR**  
**COOLTOUCH™ TRANSMITTER – BASIC**

See page 321 in our main catalog for more information

**INCLUDED CONTROL**



**WALL CONTROL SYSTEM – BASIC**

- ★ 3 Forward Speeds and Motor Off
- ★ Manual Reverse
- ★ Light On/Off with Full Range Dimming

**BLADE SPECS**

Fan Finish	Blade Finish	Part No.
<b>BSS</b> Brushed Stainless Steel	Champagne	FB300169BSS
<b>OBB</b> Oil Brushed Bronze™	Oil Brushed Bronze™	FB300169OBB
<b>WH</b> White	White	FB300169WH

**INCLUDED**

- ★ **BLADES (4)** Included ★ 12° Pitch ★ 42" Sweep Non-Reversible ★ Polycarbonate
- ★ **DOWNRODS** 4" Downrod with 1" (O.D.)
- ★ **DOWNLIGHT** Integrated. 17W Dimmable LED Platform 1,300 Lumens, 80 CRI, 3,000K CCT
- ★ **DOWNLIGHT GLASS** Etched Cased Opal
- ★ **OPTIONAL DOWNLIGHT** N/A
- ★ **UPLIGHT** N/A ★ **UPLIGHT GLASS** N/A
- ★ **LOW CEILING ADAPTABLE** No


**FAN SPECS**

- ★ **MOUNTING SLOPE – PITCH** 30° or 7/12
- ★ **LEAD WIRE** 78" ★ **cETLus LISTED** Indoor
- ★ **HANGING WEIGHT** 17.16 lbs.
- ★ **WARRANTY** Limited Lifetime

**MOTOR SPECS**

- ★ **MOTOR SIZE/ TYPE** 153mm x 15mm, AC
- ★ **AMPS** 0.34 ★ **RPM** 230 on High
- ★ **ENERGY STAR** N/A

**HANGING MEASUREMENTS**



WITH 4" DOWNROD  
**A - 14.88" B - 10.02" C - 10.63"**

**METAL CAPS**

Includes a metal fixture cap for non-light use



AIRFLOW	POWER USAGE	AIRFLOW EFFICIENCY
4125 Cubic Ft. Per Minute on High	42 Watts on High (Excludes Lights)	99 Cubic Ft. Per Minute Per Watt



**300195 OBB**  
Finish: Oil Brushed Bronze™  
Glass: Etched Cased Opal  
Blades: Medium Cherry



**300195 AP**  
Finish: Antique Pewter  
Glass: Etched Cased Opal  
Blades: Light Cherry





**OPTIONAL CONTROLS**



**337214TR**  
**COOLTOUCH™ TRANSMITTER – BASIC**

See page 321 in our main catalog for more information

**INCLUDED CONTROL**



**WALL CONTROL SYSTEM – BASIC**

- ★ 3 Forward Speeds and Motor Off
- ★ Manual Reverse
- ★ Light On/Off with Full Range Dimming

**BLADE SPECS**

Fan Finish	Blade Finish	Part No.
 AP Antique Pewter	Light Cherry	FB300195AP
	Dark Cherry	FB300195AP
 OBB Oil Brushed Bronze™	Medium Cherry	FB300195OBB
	Walnut	FB300195OBB

**INCLUDED**

- ★ **BLADES** (5) Included ★ 14° Pitch ★ 52" Sweep Reversible ★ Wood
- ★ **DOWNRODS** 4.5" Downrod with 1" (O.D.)
- ★ **DOWNLIGHT** Integrated. 17W Dimmable LED Platform 1,300 Lumens, 80 CRI, 3,000K CCT
- ★ **DOWNLIGHT GLASS** Etched Cased Opal
- ★ **OPTIONAL DOWNLIGHT** N/A
- ★ **UPLIGHT** N/A ★ **UPLIGHT GLASS** N/A
- ★ **LOW CEILING ADAPTABLE** No


**FAN SPECS**

- ★ **MOUNTING SLOPE – PITCH** 30° or 7/12
- ★ **LEAD WIRE** 78" ★ **cETLus LISTED** Indoor
- ★ **HANGING WEIGHT** 19.23 lbs.
- ★ **WARRANTY** Limited Lifetime

**MOTOR SPECS**

- ★ **MOTOR SIZE/ TYPE** 172mm x 17mm, AC
- ★ **AMPS** 0.53 ★ **RPM** 133 on High
- ★ **ENERGY STAR** N/A

**HANGING MEASUREMENTS**



WITH 4.5" DOWNROD  
 A - 14.88" B - 9.82" C - 10.50"

AIRFLOW	POWER USAGE	AIRFLOW EFFICIENCY
4801 Cubic Ft. Per Minute on High	63 Watts on High (Excludes Lights)	76 Cubic Ft. Per Minute Per Watt



60" Enthral  
300192 NI  
See pages s360-s361

## LED LIGHT KIT FANS

- LED lighting can use 50-90% less energy than traditional light sources
- Long life of LED's can be up to 4-5 times longer than traditional light sources
- Generates less heat
- Containing no toxic chemicals LED's are more environmentally friendly than traditional incandescent and fluorescent lamps

LED  
LIGHT KIT

## Energy Star CEILING FANS

- Meet strict guidelines set by the U.S. Environmental Protection Agency (EPA)
- 50% or more efficient than conventional fan/light units
- Many come with highly efficient CFL bulbs

Energy Star  
ENERGY STAR



# SELECT

---

## CEILING FANS

**Classic styles with a touch of  
modern-day refinement**

- Timeless styling
- Versatile pieces: multiple size options and reversible blades
- On-trend finishes
- Limited Lifetime Warranty, see [kichler.com](http://kichler.com) for details





**310135 WZC**  
Finish: Weathered Zinc  
Blades: Weathered Medium Oak

52"  
EADS™



**310135 NI**  
Finish: Brushed Nickel  
Blades: Walnut Shadowed  
**370044 NI**  
Light Kit: Etched Cased Opal Glass  
(Sold Separately)



**310135 OZ**  
Finish: Olde Bronze®  
Blades: Weathered Medium Oak

**OPTIONAL CONTROLS**



337001WH  
370039MUL  
337010WH/IV/ALM  
337011WH/IV/ALM  
337012WH/IV/ALM  
370032MUL

337214

**COOLTOUCH™ CONTROL SYSTEM – BASIC**

See pages 320-322 in our main catalog for more information

**INCLUDED CONTROL**

**PULL CHAIN**

- ★ 3 Forward Speeds
- ★ Manual Reverse



**BLADE SPECS**

Fan Finish	Blade Finish	Part No.
 <b>NI</b> Brushed Nickel	Walnut	FB310135NI
	Walnut Shadowed	FB310135NI
 <b>OZ</b> Olde Bronze®	Weathered Medium Oak	FB310135OZ
	Weathered Medium Oak	FB310135WZC
 <b>WZC</b> Weathered Zinc	Weathered Medium Oak	FB310135WZC

**INCLUDED**

- ★ **BLADES** (4) Included ★ 14° Pitch ★ 52" Sweep Reversible ★ Wood Veneer
- ★ **DOWNRODS** 4.5" Downrod with 1" (O.D.)
- ★ **DOWNLIGHT** N/A
- ★ **DOWNLIGHT GLASS** N/A
- ★ **OPTIONAL DOWNLIGHT** Light Kit 370044 NI, OZ, WZC or Accessory Light Kits Available. See Pages 298-311 in our Main Catalog
- ★ **UPLIGHT** N/A ★ **UPLIGHT GLASS** N/A
- ★ **LOW CEILING ADAPTABLE** No


**FAN SPECS**

- ★ **MOUNTING SLOPE – PITCH** 30° or 7/12
- ★ **LEAD WIRE** 78" ★ **cETLus LISTED** Indoor
- ★ **HANGING WEIGHT** 18.38 lbs.
- ★ **WARRANTY** Limited Lifetime

**MOTOR SPECS**

- ★ **MOTOR SIZE/ TYPE** 172mm x 17mm, AC
- ★ **AMPS** 0.64 ★ **RPM** 196 on High
- ★ **ENERGY STAR** N/A

**HANGING MEASUREMENTS**



WITH 4.5" DOWNROD  
A - 14.00" B - 11.10" C - 10.80"

AIRFLOW	POWER USAGE	AIRFLOW EFFICIENCY
5624 Cubic Ft. Per Minute on High	77 Watts on High (Excludes Lights)	73 Cubic Ft. Per Minute Per Watt

**OPTIONAL DOWNLIGHT**



**370044 NI**  
Light Kit  
Etched Cased Opal Glass  
(3) E12, 60W B-10  
Lamps Included  
6.25"H x 12.75"D



**370044 OZ**  
Light Kit  
Etched Cased Opal Glass  
(3) E12, 60W B-10  
Lamps Included  
6.25"H x 12.75"D



**370044 WZC**  
Light Kit  
Etched Cased Opal Glass  
(3) E12, 60W B-10  
Lamps Included  
6.25"H x 12.75"D

Additional downlight options can be found on pages 298-311 in our main catalog.



**300185 DBK**  
Finish: Distressed Black  
Blades: Walnut



52"  
FRYST™



**300185 OBB**  
Finish: Oil Brushed Bronze™  
Blades: Cherry



**300185 NI**  
Finish: Brushed Nickel  
Blades: Cherry





OPTIONAL CONTROLS



337001WH  
370039MUL  
337010WH/IV/ALM  
337011WH/IV/ALM  
337012WH/IV/ALM

337214

COOLTOUCH™ CONTROL SYSTEM – BASIC

See pages 320-322 in our main catalog for more information

INCLUDED CONTROL



PULL CHAIN

- ★ 3 Forward Speeds
- ★ Manual Reverse



INCLUDED

- ★ **BLADES** (5) Included ★ 12° Pitch ★ 52" Sweep Reversible ★ Wood Veneer
- ★ **DOWNRODS** 6" Downrod with 1" (O.D.)
- ★ **DOWNLIGHT** N/A
- ★ **DOWNLIGHT GLASS** N/A
- ★ **OPTIONAL DOWNLIGHT** Accessory Light Kit Available. See Pages 298-311 in our Main Catalog
- ★ **UPLIGHT** N/A ★ **UPLIGHT GLASS** N/A
- ★ **LOW CEILING ADAPTABLE** Yes, See Our Optional Flush Mouth Accessory 337008 on Page s383


FAN SPECS

- ★ **MOUNTING SLOPE – PITCH** 30° or 7/12
- ★ **LEAD WIRE** 78" ★ **cETLus LISTED** Indoor
- ★ **HANGING WEIGHT** 22.92 lbs.
- ★ **WARRANTY** Limited Lifetime

MOTOR SPECS

- ★ **MOTOR SIZE/ TYPE** 188mm x 25mm, AC
- ★ **AMPS** 0.59 ★ **RPM** 185 on High
- ★ **ENERGY STAR** Yes




HANGING MEASUREMENTS



WITH 6" DOWNROD  
A - 15.90" B - 13.40" C - 12.48"

AIRFLOW	POWER USAGE	AIRFLOW EFFICIENCY
5618 Cubic Ft. Per Minute on High	70 Watts on High (Excludes Lights)	80 Cubic Ft. Per Minute Per Watt

BLADE SPECS

Fan Finish	Blade Finish	Part No.
 <b>DBK</b> Distressed Black	Cherry	FB300185DBK
	Walnut	FB300185DBK
 <b>NI</b> Brushed Nickel	Cherry	FB300185NI
	Walnut	FB300185NI
 <b>OBB</b> Oil Brushed Bronze™	Cherry	FB300185OBB
	Walnut	FB300185OBB

OPTIONAL SOLID WOOD BLADE SETS

Sold separately. See page 318 in our main catalog for more blade options.



**371030**  
Weathered White Solid Wood



**371031**  
Shadowed Walnut Solid Wood



**371032**  
Shadowed Walnut Solid Wood




**371033**  
Shadowed Cherry Solid Wood




**300199 OZ**  
Finish: Olde Bronze®  
**370045**  
Blades: Natural Bamboo  
(Sold Separately)

52"  
KLEVER



**300199 AP**  
Finish: Antique Pewter  
**370046**  
Blades: Natural Bamboo  
(Sold Separately)



**300199 BAB**  
Finish: Burnished Antique Brass  
**370045**  
Blades: Natural Bamboo  
(Sold Separately)



OPTIONAL CONTROLS



337001WH  
370039MUL  
337010WH/IV/ALM  
337011WH/IV/ALM  
337012WH/IV/ALM

337214

COOLTOUCH™ CONTROL SYSTEM – BASIC

See pages 320-322 in our main catalog for more information

INCLUDED CONTROL



PULL CHAIN

- ★ 3 Forward Speeds
- ★ Manual Reverse

BLADE SPECS

Fan Finish



Antique Pewter




Burnished Antique Brass




Olde Bronze®

OPTIONAL NATURAL BAMBOO BLADES

Sold Separately.



370045  
Natural Bamboo Blade



370046  
Natural Bamboo Blade

INCLUDED

- ★ **BLADES** (5) Sold Separately ★ 14° Pitch ★ 52" Sweep
- Non-Reversible ★ Natural Bamboo
- ★ **DOWNRODS** 4" Downrod with 1" (O.D.)
- ★ **DOWNLIGHT** N/A
- ★ **DOWNLIGHT GLASS** N/A
- ★ **OPTIONAL DOWNLIGHT** Accessory Light Kit Available. See Pages 298-311 in our Main Catalog
- ★ **UPLIGHT** N/A ★ **UPLIGHT GLASS** N/A
- ★ **LOW CEILING ADAPTABLE** No


FAN SPECS

- ★ **MOUNTING SLOPE – PITCH** 30° or 7/12
- ★ **LEAD WIRE** 78" ★ **cETLus LISTED** Indoor
- ★ **HANGING WEIGHT** 17.05 lbs.
- ★ **WARRANTY** Limited Lifetime

MOTOR SPECS

- ★ **MOTOR SIZE/ TYPE** 172mm x 20mm, AC
- ★ **AMPS** 0.53 ★ **RPM** 100 on High
- ★ **ENERGY STAR** N/A

HANGING MEASUREMENTS



WITH 4" DOWNROD  
A - 13.76" B - 12.13" C - 9.70"

<b>AIRFLOW</b>	<b>POWER USAGE</b>	<b>AIRFLOW EFFICIENCY</b>
3327 Cubic Ft. Per Minute on High	61 Watts on High (Excludes Lights)	54 Cubic Ft. Per Minute Per Watt

NOTE: Performance Data Reflects Oval Blade Set 370045



SELECT



**300188 NI**  
Finish: Brushed Nickel  
Blades: Light Walnut

60"  
TULLE™

**OPTIONAL 70" SOLID WOOD  
ACCESSORY BLADES**

Sold separately. See page 319 in our main catalog  
for more blade options.



**371050**  
Weathered White  
Solid Wood



**371051**  
Walnut – Carved Leaf  
Solid Wood



**371052**  
Cherry Squared  
Solid Wood



**371034**  
Walnut Squared  
Solid Wood



## OPTIONAL CONTROLS



337001WH  
370039MUL  
337010WH/IV/ALM  
337011WH/IV/ALM  
337012WH/IV/ALM

337214

### COOLTOUCH™ CONTROL SYSTEM – BASIC

See pages 320-322 in our main catalog for more information

## INCLUDED CONTROL

### PULL CHAIN

- ★ 3 Forward Speeds
- ★ Manual Reverse



SELECT



## INCLUDED

- ★ **BLADES** (5) Included ★ 14° Pitch ★ 60" Sweep Reversible ★ Wood
- ★ **DOWNRODS** 4" Downrod with 1" (O.D.)
- ★ **DOWNLIGHT** N/A
- ★ **DOWNLIGHT GLASS** N/A
- ★ **OPTIONAL DOWNLIGHT** Accessory Light Kit Available. See Pages 298-311 in our Main Catalog
- ★ **UPLIGHT** N/A ★ **UPLIGHT GLASS** N/A
- ★ **LOW CEILING ADAPTABLE** Yes, See Our Optional Flush Mouth Accessory 337008 on Page s383


## FAN SPECS

- ★ **MOUNTING SLOPE – PITCH** 30° or 7/12
- ★ **LEAD WIRE** 78" ★ **cETLus LISTED** Indoor
- ★ **HANGING WEIGHT** 27.83 lbs.
- ★ **WARRANTY** Limited Lifetime

## MOTOR SPECS

- ★ **MOTOR SIZE/ TYPE** 212mm x 25mm, AC
- ★ **AMPS** 0.69 ★ **RPM** 155 on High
- ★ **ENERGY STAR** Yes

## HANGING MEASUREMENTS



WITH 4" DOWNROD  
A - 14.02" B - 11.28" C - 13.78"

## BLADE SPECS

Fan Finish	Blade Finish	Part No.
 <b>DBK</b> Distressed Black	American Walnut	FB300188DBK
	Dark Walnut	FB300188DBK
 <b>NI</b> Brushed Nickel	Light Cherry	FB300188NI
	Light Walnut	FB300188NI
 <b>OBB</b> Oil Brushed Bronze™	Light Cherry	FB300188OBB
	Walnut	FB300188OBB
 <b>TZ</b> Tannery Bronze™	Dark Cherry	FB300188TZ
	Teak	FB300188TZ
 <b>WH</b> White	White	FB300188WH

AIRFLOW	POWER USAGE	AIRFLOW EFFICIENCY
7600 Cubic Ft. Per Minute on High	82 Watts on High (Excludes Lights)	92 Cubic Ft. Per Minute Per Watt



**300188 DBK**  
Finish: Distressed Black  
Blades: American Walnut

60"

TULLE™

CONTINUED



**300188 OBB**  
Finish: Oil Brushed Bronze™  
Blades: Walnut





## OPTIONAL CONTROLS



337001WH  
370039MUL  
337010WH/IV/ALM  
337011WH/IV/ALM  
337012WH/IV/ALM

337214

### COOLTOUCH™ CONTROL SYSTEM – BASIC

See pages 320-322 in our main catalog for more information

## INCLUDED CONTROL

### PULL CHAIN

- ★ 3 Forward Speeds
- ★ Manual Reverse



SELECT



**300188 WH**

Finish: White  
Blades: White



**300188 TZ**

Finish: Tannery Bronze™  
Blades: Teak

SELECT



**300192 NI**  
Finish: Brushed Nickel  
Glass: Satin Etched  
Blades: Walnut

60"  
ENTHRALL



**300192 SNB**  
Finish: Satin Natural Bronze  
Glass: Satin Etched  
Blades: Cherry



**OPTIONAL CONTROLS**



TR300192NI  
TR300192SNB

**3-SPEED COOLTOUCH™ FULL FUNCTION TRANSMITTER**

**INCLUDED CONTROL**



**WALL CONTROL SYSTEM – FULL FUNCTION**

- ★ 3 Forward Speeds & Reverse
- ★ Lights On/Off with Full Range Dimming
- ★ Motor Off



**INCLUDED**

- ★ **BLADES** (5) Included ★ 14° Pitch ★ 60" Sweep Reversible ★ Wood
- ★ **DOWNRODS** 4" Downrod with 1" (O.D.)
- ★ **DOWNLIGHT** Integrated. 17W Dimmable LED Platform 1,300 Lumens, 80 CRI, 3,000K CCT
- ★ **DOWNLIGHT GLASS** Satin Etched
- ★ **OPTIONAL DOWNLIGHT** N/A
- ★ **UPLIGHT** N/A ★ **UPLIGHT GLASS** N/A
- ★ **LOW CEILING ADAPTABLE** No


**FAN SPECS**

- ★ **MOUNTING SLOPE – PITCH** 22° or 4/12
- ★ **LEAD WIRE** 78" ★ **cUL LISTED** Indoor
- ★ **HANGING WEIGHT** 23.17 lbs.
- ★ **WARRANTY** Limited Lifetime

**MOTOR SPECS**

- ★ **MOTOR SIZE/ TYPE** 188mm x 25mm, AC
- ★ **AMPS** 0.66 ★ **RPM** 130 on High
- ★ **ENERGY STAR** N/A

**HANGING MEASUREMENTS**



WITH 4" DOWNROD  
A - 14.22" B - 9.93" C - 12.34"

**BLADE SPECS**

Fan Finish	Blade Finish	Part No.
 NI Brushed Nickel	Cherry	FB300192NI
	Walnut	FB300192NI
 SNB Satin Natural Bronze	Cherry	FB300192SNB
	Walnut	FB300192SNB

<p><b>AIRFLOW</b></p> <p>6804 Cubic Ft. Per Minute on High</p>	<p><b>POWER USAGE</b></p> <p>80 Watts on High (Excludes Lights)</p>	<p><b>AIRFLOW EFFICIENCY</b></p> <p>85 Cubic Ft. Per Minute Per Watt</p>
--------------------------------------------------------------------	-------------------------------------------------------------------------	------------------------------------------------------------------------------



SELECT



52"  
ORRIN

**300191 NI**  
Finish: Brushed Nickel  
Glass: Satin Etched  
Blades: Cherry



**300191 SNB**  
Finish: Satin Natural Bronze  
Glass: Satin Etched  
Blades: Walnut

OPTIONAL CONTROLS



370039MULTR

WALL TRANSMITTER – BASIC

See page 321 in our main catalog for more information

INCLUDED CONTROL



COOLTOUCH™ CONTROL SYSTEM – BASIC

- ★ 3 Forward Speeds
- ★ Manual Reverse
- ★ Lights On/Off with Full Range Dimming
- ★ Motor Off



INCLUDED

- ★ **BLADES** (5) Included ★ 14° Pitch ★ 52" Sweep Reversible ★ Wood
- ★ **DOWNRODS** 4.00" Downrod with 1" (O.D.)
- ★ **DOWNLIGHT** Integrated. Uses (3) E-12, 40-W B-8 Lamps
- ★ **DOWNLIGHT GLASS** Satin Etched
- ★ **OPTIONAL DOWNLIGHT** N/A
- ★ **UPLIGHT** N/A ★ **UPLIGHT GLASS** N/A
- ★ **LOW CEILING ADAPTABLE** No


FAN SPECS

- ★ **MOUNTING SLOPE – PITCH** 22° or 4/12
- ★ **LEAD WIRE** 78" ★ **cUL LISTED** Indoor
- ★ **HANGING WEIGHT** 19.80 lbs.
- ★ **WARRANTY** Limited Lifetime

MOTOR SPECS



- ★ **MOTOR SIZE/ TYPE** 172mm x 17mm, AC
- ★ **AMPS** 0.49 ★ **RPM** 177 on High
- ★ **ENERGY STAR** N/A

HANGING MEASUREMENTS



WITH 4" DOWNROD  
A - 16.98" B - 9.98" C - 11.54"

BLADE SPECS

Fan Finish	Blade Finish	Part No.
 <b>NI</b> Brushed Nickel	Cherry	FB300191NI
	Walnut	FB300191NI
 <b>SNB</b> Satin Natural Bronze	Cherry	FB300191SNB
	Walnut	FB300191SNB

<b>AIRFLOW</b> 5307 Cubic Ft. Per Minute on High	<b>POWER USAGE</b> 60 Watts on High (Excludes Lights)	<b>AIRFLOW EFFICIENCY</b> 89 Cubic Ft. Per Minute Per Watt
--------------------------------------------------------	-------------------------------------------------------------	------------------------------------------------------------------



65" Maor Patio  
310136 WZC  
See pages s366-s367

## LED LIGHT KIT FANS

- LED lighting can use 50-90% less energy than traditional light sources
- Long life of LED's can be up to 4-5 times longer than traditional light sources
- Generates less heat
- Containing no toxic chemicals LED's are more environmentally friendly than traditional incandescent and fluorescent lamps

LED  
LIGHT KIT

## WET-Rated CEILING FANS

For open/direct exposure to sun, rain or water spray

- Ideal for pergolas, lanais, open porches and more
- Painted and powder-coated finishes
- Stainless steel mounting hardware
- Aluminum support system
- All-weather ABS plastic blade options

Wet  
LOCATION





# OUTDOOR INDOOR

---

## CEILING FANS

### DAMP-Rated CEILING FANS

Engineered for hot, high-humidity areas

- Ideal for enclosed porches, sunrooms, bathrooms and more
- Painted and powder-coated finishes
- Galvanized undercoating
- Stainless-steel mounting hardware
- All-weather ABS plastic blade or sealed wood blade options



OUTDOOR  
INDOOR



**310136 DBK**

Finish: Distressed Black  
Glass: Etched Cased Opal  
Blades: Distressed Black



**310136 OZ**

Finish: Olde Bronze®  
Glass: Etched Cased Opal  
Blades: Olde Bronze®



**310136 WZC**

Finish: Weathered Zinc  
Glass: Etched Cased Opal  
Blades: Weathered Zinc



OPTIONAL CONTROLS



370039MUL

337214

COOLTOUCH™ CONTROL SYSTEM – BASIC

See page 320 in our main catalog for more information.

NOTE: Receiver is wet rated. Transmitter for indoor use.

INCLUDED CONTROL

PULL CHAIN

- ★ 3 Forward Speeds
- ★ Manual Reverse



BLADE SPECS

Fan Finish	Blade Finish	Part No.
 <p><b>DBK</b> Distressed Black</p>	 <p>Distressed Black</p>	<p>FB310136DBK</p>
 <p><b>OZ</b> Olde Bronze®</p>	 <p>Olde Bronze®</p>	<p>FB310136OZ</p>
 <p><b>WZC</b> Weathered Zinc</p>	 <p>Weathered Zinc</p>	<p>FB310136WZC</p>

INCLUDED

- ★ **BLADES** (4) Included ★ 13° Pitch ★ 65" Sweep Non-Reversible ★ Aluminum
- ★ **DOWNRODS** 4.5" Downrod with 1" (O.D.)
- ★ **DOWNLIGHT** Integrated. 17W LED Platform 1,300 Lumens, 80 CRI, 3,000K CCT
- ★ **DOWNLIGHT GLASS** Etched Cased Opal
- ★ **OPTIONAL DOWNLIGHT** N/A
- ★ **UPLIGHT** N/A ★ **UPLIGHT GLASS** N/A
- ★ **LOW CEILING ADAPTABLE** No


FAN SPECS

- ★ **MOUNTING SLOPE – PITCH** 30° or 7/12
- ★ **LEAD WIRE** 78" ★ **cETLus LISTED** Damp
- ★ **HANGING WEIGHT** 38.58 lbs.
- ★ **WARRANTY** Limited Lifetime

MOTOR SPECS

- ★ **MOTOR SIZE/ TYPE** 212mm x 20mm, AC
- ★ **AMPS** 0.72 ★ **RPM** 137 on High
- ★ **ENERGY STAR** N/A

HANGING MEASUREMENTS



WITH 4.5" DOWNROD  
A - 17.60" B - 12.00" C - 13.00"

AIRFLOW	POWER USAGE	AIRFLOW EFFICIENCY
8803 Cubic Ft. Per Minute on High	86 Watts on High (Excludes Lights)	103 Cubic Ft. Per Minute Per Watt



OUTDOOR  
INDOOR



**310128 DBK**  
Finish: Distressed Black  
Blades: Walnut



52"  
FRYST™  
PATIO



**310128 TZP**  
Finish: Tannery Bronze™  
Blades: Cherry  
**380903 TZP**  
Light Kit: Etched Cased Opal Glass  
(Sold Separately)



## OPTIONAL CONTROLS



370039MUL  
337010WH/IV/ALM  
337012WH/IV/ALM

337214

### COOLTOUCH™ CONTROL SYSTEM – BASIC

See pages 320-322 in our main catalog for more information.  
NOTE: Receiver is wet rated. Transmitter for indoor use.

## INCLUDED CONTROL

### PULL CHAIN

- ★ 3 Forward Speeds
- ★ Manual Reverse



OUTDOOR INDOOR

## BLADE SPECS

Fan Finish	Blade Finish	Part No.
 <b>DBK</b> Distressed Black	Cherry	FB310128DBK
	Walnut	FB310128DBK
 <b>TZP</b> Tannery Bronze™ Powder Coat	Cherry	FB310128TZP
	Walnut	FB310128TZP

## CLIMATES™ ACCESSORY BLADE OPTIONS

Climates™ blade sets sold separately. See pages 316-317 in our main catalog for more blade options.



**371016** **WET**  
Walnut-Teak – Reversible All Weather ABS Blades



**370020** **WET**  
Natural Bamboo All Weather ABS Blades



**371022** **DAMP**  
Walnut Stain Solid Wood



**371100** **DAMP**  
Distressed Teak Stain Solid Wood

## INCLUDED

- ★ **BLADES** (5) Included ★ 12° Pitch ★ 52" Sweep Reversible ★ ABS
- ★ **DOWNRODS** 6" Downrod with 1" (O.D.)
- ★ **DOWNLIGHT** N/A
- ★ **DOWNLIGHT GLASS** N/A
- ★ **OPTIONAL DOWNLIGHT** Accessory Light Kit Available. See Pages 298-311 in our Main Catalog
- ★ **UPLIGHT** N/A ★ **UPLIGHT GLASS** N/A
- ★ **LOW CEILING ADAPTABLE** Yes, See Our Optional Flush Mount Accessory 337008 on Page s383


## FAN SPECS

- ★ **MOUNTING SLOPE – PITCH** 30° or 7/12
- ★ **LEAD WIRE** 78" ★ **cUL LISTED** Wet
- ★ **HANGING WEIGHT** 24.27 lbs.
- ★ **WARRANTY** Limited Lifetime

## MOTOR SPECS

- ★ **MOTOR SIZE/ TYPE** 188mm x 25mm, AC
- ★ **AMPS** 0.59 ★ **RPM** 195 on High
- ★ **ENERGY STAR** Yes

## HANGING MEASUREMENTS



WITH 6" DOWNROD  
A - 15.90" B - 13.40" C - 12.48"

### AIRFLOW

6108  
Cubic Ft. Per Minute on High

### POWER USAGE

71  
Watts on High (Excludes Lights)

### AIRFLOW EFFICIENCY

86  
Cubic Ft. Per Minute Per Watt

OUTDOOR  
INDOOR



**310117 TZP**  
Finish: Tannery Bronze™ Powder Coat  
Glass: Fresnel Lens  
Blades: Light Walnut

60"  
HATTERAS  
BAY™  
PATIO



**310117 WCP**  
Finish: Weathered Copper™ Powder Coat  
Glass: Fresnel Lens  
Blades: Medium Walnut



**310117 DBK**  
Finish: Distressed Black  
Glass: Fresnel Lens  
Blades: Cherry



**310117 WZC**  
Finish: Weathered Zinc  
Glass: Fresnel Lens  
Blades: Dark Walnut





**OPTIONAL CONTROLS**



TR310117DBK  
TR310117TZP  
TR310117WCP  
TR310117WZC

**3-SPEED COOLTOUCH™ FULL FUNCTION TRANSMITTER**

NOTE: Receiver is Wet Rated. Transmitter for Indoor Use.

**INCLUDED CONTROL**



**WALL CONTROL SYSTEM – FULL FUNCTION**

- ★ 3 Forward Speeds and Reverse
- ★ Light On/Off with Full Range Dimming
- ★ Motor Off
- ★ Receiver Included



**INCLUDED**

- ★ **BLADES** (5) Included ★ 12° Pitch ★ 60" Sweep Reversible ★ ABS
- ★ **DOWNRODS** 6" Downrod with 1" (O.D.)
- ★ **DOWNLIGHT** Yes. Integrated. Uses (4) E-12 40W B-10.5
- ★ **DOWNLIGHT GLASS** Fresnel Lens
- ★ **OPTIONAL DOWNLIGHT** N/A
- ★ **UPLIGHT** N/A ★ **UPLIGHT GLASS** N/A
- ★ **LOW CEILING ADAPTABLE** Yes, Flush Mount Canopy Included.


**FAN SPECS**

- ★ **MOUNTING SLOPE – PITCH** 22° or 4/12
- ★ **LEAD WIRE** 78" ★ **cUL LISTED** Damp
- ★ **HANGING WEIGHT** 32.36 lbs.
- ★ **WARRANTY** Limited Lifetime

**MOTOR SPECS**

- ★ **MOTOR SIZE/ TYPE** 188mm x 25mm, AC
- ★ **AMPS** 0.57 ★ **RPM** 150 on High
- ★ **ENERGY STAR** N/A

**HANGING MEASUREMENTS**



WITH 6" DOWNROD  
A - 17.52" B - 12.90" C - 15.36"

**BLADE SPECS**

Fan Finish	Blade Finish	Part No.
<p><b>DBK</b> Distressed Black</p>	Cherry	FB310117DBK
	Light Walnut	FB310117DBK
<p><b>TZP</b> Tannery Bronze™ Powder Coat</p>	Cherry	FB310117TZP
	Light Walnut	FB310117TZP
<p><b>WCP</b> Weathered Copper™ Powder Coat</p>	Dark Walnut	FB310117WCP
	Medium Walnut	FB310117WCP
<p><b>WZC</b> Weathered Zinc</p>	Dark Walnut	FB310117WZC
	Medium Walnut	FB310117WZC

<p><b>AIRFLOW</b></p> <p>6665 Cubic Ft. Per Minute on High</p>	<p><b>POWER USAGE</b></p> <p>69 Watts on High (Excludes Lights)</p>	<p><b>AIRFLOW EFFICIENCY</b></p> <p>97 Cubic Ft. Per Minute Per Watt</p>
--------------------------------------------------------------------	-------------------------------------------------------------------------	------------------------------------------------------------------------------

OUTDOOR  
INDOOR



**310193 TZP**  
Finish: Tannery Bronze™  
Blades: Light Walnut

60"

TULLE™  
PATIO



**310193 WSP**  
Finish: Weathered Steel  
Blades: Teak  
**380020 WSP**  
Light Kit: Etched Cased Opal Glass  
(Sold Separately)



**310193 WCP**  
Finish: Weathered Copper  
Blades: Medium Walnut



**OPTIONAL CONTROLS**



370039MUL  
337010WH/IV/ALM  
337012WH/IV/ALM

337214

**COOLTOUCH™ CONTROL SYSTEM – BASIC**

See pages 320-322 in our main catalog for more information.  
NOTE: Receiver is wet rated. Transmitter for indoor use.

**INCLUDED CONTROL**

**PULL CHAIN**

- ★ 3 Forward Speeds
- ★ Manual Reverse



**BLADE SPECS**

Fan Finish	Blade Finish	Part No.
TZP Tannery Bronze™	Cherry	FB310193TZP
	Light Walnut	FB310193TZP
WCP Weathered Copper	Medium Walnut	FB310193WCP
	Dark Walnut	FB310193WCP
WSP Weathered Steel	Teak	FB310193WSP
	Light Walnut	FB310193WSP



**INCLUDED**

- ★ **BLADES** (5) Included ★ 14° Pitch ★ 60" Sweep Reversible ★ ABS
- ★ **DOWNRODS** 4" Downrod with 1" (O.D.)
- ★ **DOWNLIGHT** N/A
- ★ **DOWNLIGHT GLASS** N/A
- ★ **OPTIONAL DOWNLIGHT** Accessory Light Kit Available. See Pages 298-311 in our Main Catalog
- ★ **UPLIGHT** N/A ★ **UPLIGHT GLASS** N/A
- ★ **LOW CEILING ADAPTABLE** Yes, See Our Optional Flush Mount Accessory 337008 on Page s383


**FAN SPECS**

- ★ **MOUNTING SLOPE – PITCH** 30° or 7/12
- ★ **LEAD WIRE** 78" ★ **cUL LISTED** Wet
- ★ **HANGING WEIGHT** 29.81 lbs.
- ★ **WARRANTY** Limited Lifetime

**MOTOR SPECS**

- ★ **MOTOR SIZE/ TYPE** 212mm x 25mm, AC
- ★ **AMPS** 0.75 ★ **RPM** 178 on High
- ★ **ENERGY STAR** Yes

**HANGING MEASUREMENTS**



WITH 4" DOWNROD  
A - 14.02" B - 11.28" C - 13.78"

AIRFLOW	POWER USAGE	AIRFLOW EFFICIENCY
8456 Cubic Ft. Per Minute on High	84 Watts on High (Excludes Lights)	101 Cubic Ft. Per Minute Per Watt

**CLIMATES™ ACCESSORY BLADE OPTIONS**

Climates™ blade sets sold separately. See pages 316-317 in our main catalog for more blade options.





OUTDOOR  
INDOOR

52"

RENEW™  
SELECT  
PATIO



**339516 SBK**

Finish: Satin Black

Glass: Cased Opal

Blades: Satin Natural Black



**339516 TZP**

Finish: Tannery Bronze™

Glass: Cased Opal

Blades: Brown



**339516 WH**

Finish: White

Glass: Cased Opal

Blades: White



## OPTIONAL CONTROLS




370039MUL  
337010WH/IV/ALM  
337011WH/IV/ALM  
337012WH/IV/ALM

337214

### COOLTOUCH™ CONTROL SYSTEM – BASIC

See pages 320-322 in our main catalog for more information.  
NOTE: Receiver is wet rated.  
Transmitter for indoor use.



## INCLUDED

- ★ **BLADES** (5) Included ★ 12° Pitch ★ 52" Sweep Reversible ★ ABS
- ★ **DOWNRODS** 4" Downrod with 1" (O.D.)
- ★ **DOWNLIGHT** Removable. (2) 13W E-26 CFL
- ★ **DOWNLIGHT GLASS** Cased Opal
- ★ **OPTIONAL DOWNLIGHT** Accessory Light Kit Available. See Pages 298-311 in our Main Catalog
- ★ **UPLIGHT** N/A ★ **UPLIGHT GLASS** N/A
- ★ **LOW CEILING ADAPTABLE** Yes, Flush Mount Canopy Included


## FAN SPECS

- ★ **MOUNTING SLOPE – PITCH** 22° or 4/12
- ★ **LEAD WIRE** 78" ★ **cUL LISTED** Wet
- ★ **HANGING WEIGHT** 15.72 lbs.
- ★ **WARRANTY** Limited Lifetime

## MOTOR SPECS

- ★ **MOTOR SIZE/ TYPE** 153mm x 15mm, AC
- ★ **AMPS** 0.59 ★ **RPM** 179 on High
- ★ **ENERGY STAR** N/A

## HANGING MEASUREMENTS



WITH 4" DOWNROD  
A - 19.21" B - 11.02" C - 11.74"

FLUSH MOUNT  
A - 15.81" B - 7.62" C - 11.74"

### AIRFLOW

5409  
Cubic Ft. Per  
Minute on High

### POWER USAGE

68  
Watts on High  
(Excludes Lights)

### AIRFLOW EFFICIENCY

80  
Cubic Ft. Per  
Minute Per Watt




## INCLUDED CONTROL

### PULL CHAIN

- ★ 3 Forward Speeds
- ★ Manual Reverse



## BLADE SPECS

Fan Finish	Blade Finish	Part No.
 <p><b>SBK</b> Satin Black</p>	 <p>Satin Natural Black FB339516SBK</p>	
 <p><b>TZP</b> Tannery Bronze™</p>	 <p>Brown FB339516TZP</p>	
 <p><b>WH</b> White</p>	 <p>White FB339516WH</p>	





Klever™  
300199 OZ  
Shown with 370045 Blades  
(Sold Separately)  
See pages s354-s355


## Light Kits & Glass

- Customize your Kichler ceiling fan
- Choose from a variety of decorative glass options and lighting configurations



## Blades

- Create a more customized and unique look with decorative blade options







# ACCESSORIES

## Controls

From multi-function wall transmitters to hand-held remotes that are easy-to-operate, Kichler offers you total control



## LIGHTING COMPONENT SELECTION GUIDE

# STEP 1

## SELECT GLASS

(See pages 299-301 in our main catalog for complete bowl glass options.)



**340001**  
Art Glass Bowl  
4.75" Height, 11.75" Diameter



**340002**  
Edenvale™ Etched Golden Antique Glass Bowl  
4.25" Height, 12.25" Diameter

# STEP 2

## SELECT FITTER

### FLUORESCENT



**350003**  
Decorative Fluorescent Lamp Bowl Fitter.  
2-Light, E-26 CFL 13-W. Lamps Included.  
White Finial Included. 6.00" Height, 8.75"  
Diameter. cUL Indoor.

### INCANDESCENT



**350020**  
Decorative Incandescent Lamp Bowl Fitter.  
2-Light, 75-W. E11 Halogen Mini-Can Lamp  
Included. White Finial Included. 6.00" Height,  
5.25" Diameter. cUL Indoor.

# STEP 3

## SELECT FINIAL KIT



**337006 AP**  
Antique Pewter

**337006 BSS**  
Brushed Stainless Steel

**337006 DBK**  
Distressed Black

**337006 MDW**  
Mediterranean Walnut™

**337006 NI**  
Brushed Nickel

**337006 OBB**  
Oil Brushed Bronze™

**337006 OZ**  
Olde Bronze

**337006 SNW**  
Satin Natural White

**337006 TZ**  
Tannery Bronze™

**337006 TZP**  
Tannery Bronze™ Powder  
Coat

**337006 WH**  
Powder Coat White



## GLASS BOWLS

See page s378 for the required components.



**340013**  
Satin Etched Cased Opal, 4.00" Height, 11.00" Diameter



**340014**  
Umber Etched, 4.00" Height, 11.00" Diameter



**340015**  
Alabaster Swirl, 4.00" Height, 11.00" Diameter



**340016**  
White Vetro Mica, 4.00" Height, 11.00" Diameter



**340017**  
Cased White Water, 4.00" Height, 11.00" Diameter

## 4-LIGHT MEDIUM BASE FITTER



**350110 NI**  
(shown)

- Designed to accommodate 2-1/4" Fitter Glass (sold separately). See pages 304-305 in our main catalog for the complete glass selection.
- Uses, (4), E-26 13-Watt CFL's
- Lamps Included
- 6.75" x 3.75"
- Threaded Nord Sockets
- Includes Retainer Nut Tool for Easy Assembly of Glass Shades
- cUL LISTED Indoor
- Available in finishes:
 

<b>AP</b> Antique Pewter	<b>SNB</b> Satin Natural Bronze
<b>DBK</b> Distressed Black	<b>SNW</b> Satin Natural White
<b>NI</b> Brushed Nickel	<b>TZ</b> Tannery Bronze™
<b>OBB</b> Oil Brushed Bronze™	<b>WH</b> White

**NOTE:** U.S. Sales Only

## 2-1/4" FITTER GLASS

Light fitters sold separately. See pages s379 and 302-303 in the main catalog for light fitter options.

**340010**  
Satin Etched Cased Opal  
5.25" Height,  
5.00" Width



**340011**  
White Vetro Mica  
5.25" Height,  
5.00" Width



**340012**  
Cased White Water  
5.25" Height,  
5.00" Width





DECORATIVE INCANDESCENT LIGHT FIXTURES

INCANDESCENT



- Etched Cased Opal
- Uses (3), E-12, 60-W
- Lamps Included
- 6.25" Height, 12.75" Diameter
- cUL LISTED Indoor
- Available in finishes:  
**NI** Brushed Nickel  
**OZ** Olde Bronze®  
**WZC** Weathered Zinc

**370044 WZC**  
(shown)

INCANDESCENT



- Uses (3), E-12, 40-W Edison Bulbs
- Lamps Included
- 6.75" Height, 10.25" Diameter
- cUL LISTED Indoor
- Available in finishes:  
**DBK** Distressed Black  
**NI** Brushed Nickel  
**OBB** Oil Brushed Bronze™  
**TZ** Tannery Bronze™  
**SBK** Satin Black  
**SNW** Satin Natural White  
**WH** White

**370041 DBK**  
(shown)



LED



**338200 NI**  
(shown)

- 17-Watt Dimmable LED Platform 1,300 Lumens, 80 CRI, 3,000 CCT
- Lamps Included
- 4.25" Height, 11.50" Diameter
- cETLus LISTED Indoor
- Available in finishes:  
**AP** Antique Pewter  
**DBK** Distressed Black  
**NI** Brushed Nickel  
**OBB** Oil Brushed Bronze™  
**SNB** Satin Natural Bronze  
**SNW** Satin Natural White  
**TZ** Tannery Bronze™  
**WH** White

Hard wire wall controls not recommended for use with this LED Light Kit.

INCANDESCENT



**338104 MUL**  
(shown)

- Alabaster Swirl
- Uses (2) E-11, 75-W, JD Halogen Lamps
- Lamps Included
- 5.50" Height, 12.50" Diameter
- cUL LISTED Indoor
- Included finishes:  
**NI** Brushed Nickel  
**OBB** Oil Brushed Bronze™  
**SNW** Satin Natural White  
**TZ** Tannery Bronze™  
**WH** White

## OUTDOOR/INDOOR LIGHT FIXTURES



### FLUORESCENT



**380910 ANS**  
(shown)

- For use with Canfield, Lehr, Lehr II & Yur Climates outdoor/indoor ceiling fans
- ABS Fixture and Cased Opal Glass
- Uses (1) GU24 18-Watt CFL Lamp
- Lamp Included
- 4.50" Height, 11.00" Diameter
- cUL LISTED Wet
- Available in finishes:  
**ANS** Antique Satin Silver  
**CMO** Coffee Mocha  
**DBK** Distressed Black **NEW**  
**SBK** Satin Black  
**SNW** Satin Natural White  
**WH** White **NEW**

### INCANDESCENT



**380020 ANS**  
(shown)

- Etched Cased Opal Glass
- Uses (2), E-11, 50-W JD Halogen Lamps
- Lamps Included
- 4.25" Height, 11.38" Diameter
- cUL LISTED Wet
- Decorative Low Profile Fixture
- Available in finishes:  
**ANS** Antique Satin Silver **NEW**  
**AP** Antique Pewter  
**BSS** Brushed Stainless Steel  
**CMO** Coffee Mocha **NEW**  
**DBK** Distressed Black  
**MDW** Mediterranean Walnut™  
**NI** Brushed Nickel  
**OBB** Oil Brushed Bronze™

- SBK** Satin Black
- SNB** Satin Natural Bronze
- SNW** Satin Natural White
- TZ** Tannery Bronze™
- TZP** Tannery Bronze™ Powder Coat
- WCP** Weathered Copper Powder Coat
- WSP** Weathered Steel Powder Coat
- WH** White Powder Coat



### FLUORESCENT



**338050 ANS**  
(shown)

- Cased Opal Glass
- Uses (2) E-26, 13-Watt CFL Lamps
- Lamps Included
- 5.50" Height, 10.25" Diameter
- cUL LISTED Wet
- Available in finishes:  
**ANS** Antique Satin Silver **NEW**  
**CMO** Coffee Mocha **NEW**  
**DBK** Distressed Black **NEW**  
**SBK** Satin Black  
**SNW** Satin Natural White

- TZP** Tannery Bronze™ Powder Coat
- WCP** Weathered Copper Powder Coat
- WSP** Weathered Steel Powder Coat
- WH** White Powder Coat

## CLIMATES™ WET BLADE OPTIONS



**371024**  
Satin Natural White – Non-Reversible  
All Weather ABS Blades  
52" Blade Sweep



**371025**  
Satin Natural White – Non-Reversible  
All Weather ABS Blades  
52" Blade Sweep



See pages 316-317 in our K414 catalog for Climates Wet Blade options.  
NOTE: Screw packs included with blade sets.

## 52" ACCESSORY BLADE OPTIONS

For use exclusively with Kichler® ceiling fans: 52" Canfield™ (300117), 52" Canfield Pro™ (337016), 52" Duvall™ (300178), 52" Rokr™ (300179) and 52" Fryst™ (300185).



**370050**  
Shadowed Walnut



**371070**  
Distressed White

See pages 318 in our K414 catalog for 52" Accessory Blade options.  
NOTE: Screw packs included with blade sets.

## AC CONTROL SYSTEMS

Includes transmitter and receiver.



**371042 MUL** NEW  
**WALL CONTROL SYSTEM – BASIC**

- Designed for AC Fans
- Includes Transmitter and Canopy mounted receiver
- Learn mode canopy receiver with 56,000 code settings included
- Receiver designed for wet locations
- 3 Forward speeds and motor off
- Manual Reverse
- Lights On/Off with full range dimming
- Includes white, ivory & almond switch and cover plates
- Transmitter to be placed indoors



**371045 MUL** NEW  
**WALL CONTROL SYSTEM – FULL FUNCTION**

- Designed for AC Fans
- Includes Transmitter and Canopy mounted receiver
- Learn mode canopy receiver with 56,000 code settings included
- Receiver designed for wet locations
- 3 Forward speeds, reverse and motor off
- Lights On/Off with full range dimming
- Includes white, ivory & almond switch and cover plates
- Transmitter to be placed indoors



**4 SPEED ROTARY WALL CONTROL** NEW  
**370040**

- Controls Multiple Fans on one circuit
- Max 10 AMP
- For use with most AC ceiling fans
- Brushed Aluminum faceplate with black control knob



## 60° SLOPE ADAPTER

For sloped or vaulted ceilings up to 60°.



30°



45°



60°



### SLOPE ADAPTER FEATURES

- Adapts to ceilings from 0° to 60° of slope
- Accepts our CoolTouch™ Receiver Unit for Remote Controlled Fans
- Includes "Stabilized" Mounting System
- Safety features prevent fan from "lifting" off mounting system
- Heavy Duty design features two (2) safety pins and one (1) set screw for maximum safety
- Designed for Indoor or Outdoor use
- Outdoor Finishes are Powder Coated or Painted with a Galvanized under-coating.
- Designed for use with 1" O.D. downrods ONLY
- Available in all Kichler fan finishes
- Unit does not include downrod (must be ordered separately)
- U.S. Patent Pending

All Kichler ceiling fans come standard with our universal hanging system. This basic system allows for mounting on ceilings with up to a 60° slope. **Recommended for fan stability in high wind applications (For any slope ceilings)**

### Adapter Finishes

- |                                                                   |                                         |                                                        |
|-------------------------------------------------------------------|-----------------------------------------|--------------------------------------------------------|
| <b>337005 ANS</b> Antique Satin Silver                            | <b>337005 MCH</b> Midnight Chrome       | <b>337005 SNW</b> Satin Natural White                  |
| <b>337005 AP</b> Antique Pewter<br>(Also for use with BAP finish) | <b>337005 MDW</b> Mediterranean Walnut™ | <b>337005 TZ</b> Tannery Bronze™                       |
| <b>337005 AW</b> Aged White                                       | <b>337005 NI</b> Brushed Nickel         | <b>337005 TZG</b> Tannery Bronze™ with Gold Highlights |
| <b>337005 BAB</b> Burnished Antique Brass                         | <b>337005 OBB</b> Oil Brushed Bronze™   | <b>337005 TZP</b> Tannery Bronze™ Powder Coat          |
| <b>337005 BKZ</b> Berkshire Bronze™                               | <b>337005 OI</b> Olde Iron              | <b>337005 WCP</b> Weathered Copper Powder Coat         |
| <b>337005 BSS</b> Brushed Stainless Steel                         | <b>337005 OLZ</b> Oiled Bronze          | <b>337005 WSP</b> Weathered Steel Powder Coat          |
| <b>337005 CMO</b> Coffee Mocha                                    | <b>337005 OZ</b> Olde Bronze®           | <b>337005 WH</b> White                                 |
| <b>337005 CZ</b> Carré Bronze®                                    | <b>337005 PN</b> Polished Nickel        | <b>337005 WZC</b> Weathered Zinc <b>NEW</b>            |
| <b>337005 DBK</b> Distressed Black                                | <b>337005 SBK</b> Satin Black           |                                                        |
| <b>337005 GST</b> Galvanized Steel                                | <b>337005 SNB</b> Satin Natural Bronze  |                                                        |

## FLUSH MOUNT KITS AND DOWNROD COUPLER

### FLUSH MOUNT KIT



- |                                                                      |                                                   |
|----------------------------------------------------------------------|---------------------------------------------------|
| <b>337008 AP</b><br>Antique Pewter<br>(Also for use with BAP finish) | <b>337008 OLZ</b><br>Oiled Bronze                 |
| <b>337008 AW</b><br>Aged White                                       | <b>337008 OZ</b><br>Olde Bronze®                  |
| <b>337008 BAB</b><br>Burnished Antique Brass                         | <b>337008 PN</b><br>Polished Nickel               |
| <b>337008 BSS</b><br>Brushed Stainless Steel                         | <b>337008 SBK</b><br>Satin Black                  |
| <b>337008 DBK</b><br>Distressed Black                                | <b>337008 SNB</b><br>Satin Natural Bronze         |
| <b>337008 GST</b><br>Galvanized Steel                                | <b>337008 SNW</b><br>Satin Natural White          |
| <b>337008 MCH</b><br>Midnight Chrome                                 | <b>337008 TZ</b><br>Tannery Bronze™               |
| <b>337008 MDW</b><br>Mediterranean Walnut™                           | <b>337008 TZP</b><br>Tannery Bronze™ Powder Coat  |
| <b>337008 NI</b><br>Brushed Nickel                                   | <b>337008 WCP</b><br>Weathered Copper Powder Coat |
| <b>337008 OBB</b><br>Oil Brushed Bronze™                             | <b>337008 WSP</b><br>Weathered Steel Powder Coat  |
|                                                                      | <b>337008 WH</b><br>White                         |
|                                                                      | <b>337008 WZC</b> <b>NEW</b><br>Weathered Zinc    |








### DOWNROD COUPLER



- |                                                                      |                                            |                                                           |
|----------------------------------------------------------------------|--------------------------------------------|-----------------------------------------------------------|
| <b>337007 AP</b><br>Antique Pewter<br>(Also for use with BAP finish) | <b>337007 MCH</b><br>Midnight Chrome       | <b>337007 TZG</b><br>Tannery Bronze™ with Gold Highlights |
| <b>337007 AW</b><br>Aged White                                       | <b>337007 MDW</b><br>Mediterranean Walnut™ | <b>337007 TZP</b><br>Tannery Bronze™ Powder Coat          |
| <b>337007 BAB</b><br>Burnished Antique Brass                         | <b>337007 NI</b><br>Brushed Nickel         | <b>337007 WCP</b><br>Weathered Copper Powder Coat         |
| <b>337007 BKZ</b><br>Berkshire Bronze™                               | <b>337007 OBB</b><br>Oil Brushed Bronze™   | <b>337007 WH</b><br>White                                 |
| <b>337007 BSS</b><br>Brushed Stainless Steel                         | <b>337007 OI</b><br>Olde Iron              | <b>337007 WSP</b><br>Weathered Steel Powder Coat          |
| <b>337007 CZ</b><br>Carré Bronze®                                    | <b>337007 OLZ</b><br>Oiled Bronze          | <b>337008 WZC</b> <b>NEW</b><br>Weathered Zinc            |
| <b>337007 DBK</b><br>Distressed Black                                | <b>337007 OZ</b><br>Olde Bronze®           |                                                           |
| <b>337007 GST</b><br>Galvanized Steel                                | <b>337007 PN</b><br>Polished Nickel        |                                                           |
|                                                                      | <b>337007 SBK</b><br>Satin Black           |                                                           |
|                                                                      | <b>337007 SNB</b><br>Satin Natural Bronze  |                                                           |
|                                                                      | <b>337007 SNW</b><br>Satin Natural White   |                                                           |
|                                                                      | <b>337007 TZ</b><br>Tannery Bronze™        |                                                           |

## DUAL THREADED DOWNRODS








Extension downrods 1" (O.D). Not for use with Kichler Basic and Climates fans.

CEILING HEIGHT	9 FT.	10 FT.	11 FT.	12 FT.	13 FT.	14 FT.	15 FT.
<b>SUGGESTED DOWNROD LENGTH</b>	12 IN. 	18 IN. 	24 IN. 	36 IN. 	48 IN. 	60 IN. 	72 IN. 
<b>FINISH</b>							
<b>AP</b> – Antique Pewter (Also for use with BAP finish)	360000 AP	360001 AP	360002 AP	360003 AP	360004 AP	360005 AP	360006 AP
<b>AW</b> Aged White	360000 AW	360001 AW	360002 AW	360003 AW	360004 AW	360005 AW	360006 AW
<b>BAB</b> Burnished Antique Brass	360000 BAB	360001 BAB	360002 BAB	360003 BAB	360004 BAB	360005 BAB	360006 BAB
<b>BKZ</b> Berkshire Bronze™	360000 BKZ	360001 BKZ	360002 BKZ	360003 BKZ	360004 BKZ	360005 BKZ	360006 BKZ
<b>BSS</b> Brushed Stainless Steel	360000 BSS	360001 BSS	360002 BSS	360003 BSS	360004 BSS	360005 BSS	360006 BSS
<b>CZ</b> Carré Bronze®	360000 CZ	360001 CZ	360002 CZ	360003 CZ	360004 CZ	360005 CZ	360006 CZ
<b>DBK</b> Distressed Black	360000 DBK	360001 DBK	360002 DBK	360003 DBK	360004 DBK	360005 DBK	360006 DBK
<b>GST</b> Galvanized Steel	360000 GST	360001 GST	360002 GST	360003 GST	360004 GST	360005 GST	360006 GST
<b>MCH</b> Midnight Chrome	360000 MCH	360001 MCH	360002 MCH	360003 MCH	360004 MCH	360005 MCH	360006 MCH
<b>MDW</b> Mediterranean Walnut™	360000 MDW	360001 MDW	360002 MDW	360003 MDW	360004 MDW	360005 MDW	360006 MDW
<b>NI</b> Brushed Nickel	360000 NI	360001 NI	360002 NI	360003 NI	360004 NI	360005 NI	360006 NI
<b>OBB</b> Oil Brushed Bronze™	360000 OBB	360001 OBB	360002 OBB	360003 OBB	360004 OBB	360005 OBB	360006 OBB
<b>OI</b> Olde Iron	360000 OI	360001 OI	360002 OI	360003 OI	360004 OI	360005 OI	360006 OI
<b>OLZ</b> Oiled Bronze	360000 OLZ	360001 OLZ	360002 OLZ	360003 OLZ	360004 OLZ	360005 OLZ	360006 OLZ
<b>OZ</b> Olde Bronze®	360000 OZ	360001 OZ	360002 OZ	360003 OZ	360004 OZ	360005 OZ	360006 OZ
<b>PN</b> Polished Nickel	360000 PN	360001 PN	360002 PN	360003 PN	360004 PN	360005 PN	360006 PN
<b>SBK</b> Satin Black Powder Coat	360000 SBK	360001 SBK	360002 SBK	360003 SBK	360004 SBK	360005 SBK	360006 SBK
<b>SNB</b> Satin Natural Bronze	360000 SNB	360001 SNB	360002 SNB	360003 SNB	360004 SNB	360005 SNB	360006 SNB
<b>SNW</b> Satin Natural White	360000 SNW	360001 SNW	360002 SNW	360003 SNW	360004 SNW	360005 SNW	360006 SNW
<b>TZ</b> Tannery Bronze™	360000 TZ	360001 TZ	360002 TZ	360003 TZ	360004 TZ	360005 TZ	360006 TZ
<b>TZG</b> Tannery Bronze™ with Gold	360000 TZG	360001 TZG	360002 TZG	360003 TZG	360004 TZG	360005 TZG	360006 TZG
<b>TZP</b> Tannery Bronze™ Powder Coat	360000 TZP	360001 TZP	360002 TZP	360003 TZP	360004 TZP	360005 TZP	360006 TZP
<b>WCP</b> Weathered Copper Powder Coat	360000 WCP	360001 WCP	360002 WCP	360003 WCP	360004 WCP	360005 WCP	360006 WCP
<b>WH</b> White Powder Coat	360000 WH	360001 WH	360002 WH	360003 WH	360004 WH	360005 WH	360006 WH
<b>WSP</b> Weathered Steel Powder Coat	360000 WSP	360001 WSP	360002 WSP	360003 WSP	360004 WSP	360005 WSP	360006 WSP
<b>WZC</b> Weathered Zinc <span style="background-color: #0070C0; color: white; padding: 2px;">NEW</span>	360000 WZC	360001 WZC	360002 WZC	360003 WZC	360004 WZC	360005 WZC	360006 WZC

## CLIMATES™ ALUMINUM DUAL THREADED DOWNRODS

Climates™ downrods are constructed from a durable aluminum that's designed to support fan weight and perfectly matches our Climates™ fan finishes.



CEILING HEIGHT	9 FT.	10 FT.	11 FT.	12 FT.	13 FT.	14 FT.	15 FT.
<b>SUGGESTED DOWNROD LENGTH</b>	12 IN. 	18 IN. 	24 IN. 	36 IN. 	48 IN. 	60 IN. 	72 IN. 
<b>FINISH</b>							
<b>ANS</b> Antique Satin Silver	360100 ANS	360110 ANS	360120 ANS	360130 ANS	360140 ANS	360160 ANS	360172 ANS
<b>CMO</b> Coffee Mocha	360100 CMO	360110 CMO	360120 CMO	360130 CMO	360140 CMO	360160 CMO	360172 CMO
<b>DBK</b> Distressed Black	360100 DBK	360110 DBK	360120 DBK	360130 DBK	360140 DBK	360160 DBK	360172 DBK
<b>SBK</b> Satin Natural Black	360100 SBK	360110 SBK	360120 SBK	360130 SBK	360140 SBK	360160 SBK	360172 SBK
<b>SNW</b> Satin Natural White	360100 SNW	360110 SNW	360120 SNW	360130 SNW	360140 SNW	360160 SNW	360172 SNW
<b>WH</b> White	360100 WH	360110 WH	360120 WH	360130 WH	360140 WH	360160 WH	360172 WH

## 45° BASICS SLOPE ADAPTER

Designed for use with Basics Ceiling Fans.

- Adapter finishes:
  - 471NI** Brushed Nickel
  - 471SBK** Satin Black
  - 471SNB** Satin Natural Bronze
  - 471SNW** Satin Natural White
  - 471WH** White




**471 SBK**  
(shown)



# LIGHT BULB REFERENCE

## Incandescent and Compact Fluorescent Light Bulbs



Product ID	Incandescent Light Bulb Description	
4062 CLR	E-12 40W, B8 Clear Replacement Lamp	
4063 CLR	E-12 40W, B10 Clear Replacement Lamp	
4064 CLR	E-12 60W, B10 Clear Replacement Lamp	
4088 CLR	E-12 60W, G16.5 Clear Replacement Lamp	
4069 CLR	E-12 15W, C7 Clear Replacement Lamp	
4070 CLR	E-12 10W, C7 Clear Replacement Lamp	
4060 CLR	E-12 7W, C7 Clear Replacement Lamp	
4058 CLR	E-12 40W, Antique Decorative Lamp	

Product ID	Fluorescent Light Bulb Description	
4055	22W T9 Circline G10q Base Replacement Lamp	
4056	22W G10q Replacement Ballast	
4043	13W GU24 Replacement Ballast	
4051	18W GU24 Squat Replacement Ballast	
4052	13W E26 Replacement Ballast	

Product ID	Halogen Light Bulb Description	
5925 CLR	100W J Type Halogen Replacement Lamp	
5920 FST	50W E-11 Halogen T3 Replacement Lamp	
5910 CLR	75W E-11 Halogen T3 Replacement Lamp	
5902 CLR	50W GU10 Halogen T3 Replacement Lamp	
5903 CLR	100W E-11 Halogen T3 Replacement Lamp	
5907 FST	40W E-12 Krypton T3 Replacement Lamp	
5919 FST	50W E-12 Krypton T3 Replacement Lamp	
5905 FST	60W E-12 Krypton T3 Replacement Lamp	

### Equivalent Light Output

To determine which qualified CFL light bulbs will provide the same amount of light as your current incandescent light bulbs, consult the following chart:

Incandescent Light Bulbs Watts (W)	Incandescent Minimum Light Bulbs Lumens	Common CFL Light Bulbs Watts (W)
40	450	9-13
60	800	13-15
75	1,100	18-25
100	1,600	23-30
150	2,600	30-52

- Lamps are included with all light kits.
- Wattages stated are the maximum recommended, however, you may use lower wattage lamps to suit your lighting needs.
- Finishes for fixtures installed outdoors are subject to change due to prolonged exposure to sunlight, airborne pollutants and other forms of weathering.
- All electrical products are rated as 120-volt, AC unless otherwise noted.
- All electrical products are certified and listed to UL/CSA/ETL Standards for use in U.S.A. and Canada.
- All products featured in the outdoor section are certified and listed to UL/CSA standards for wet or damp location except where noted.
- To serve you better, Kichler® reserves the right to make improvements to the products in this catalog. Therefore, some products may change during the life of the catalog and the product information contained in this catalog may also have changed.
- Kichler® Lighting Products are not produced or associated with any Native American Indians, nor are they a Native American product or the product of a particular Indian, Indian tribe or Indian arts and crafts organization as defined by 25 U.S.C. §305 et. seq.

We go to great lengths to assure the metal and glass finishes shown in the catalog match the actual products, but printing variations and variations in chemical finishes and the nature of hand applied finishing will cause some differences between the printed images and actual product, and from one product to another.



## INDEX

471.....	Pg s385	300199.....	Pg s354	360000.....	Pg s384
4043.....	Pg s386	300209.....	Pg s338	360001.....	Pg s384
4051.....	Pg s386	300230.....	Pg s340	360002.....	Pg s384
4052.....	Pg s386	310117.....	Pg s336, 370	360003.....	Pg s384
4055.....	Pg s386	310128.....	Pg s368	360004.....	Pg s384
4056.....	Pg s386	310135.....	Pg s350	360005.....	Pg s384
4058.....	Pg s386	310136.....	Pg s334, 366	360006.....	Pg s384
4060.....	Pg s386	310193.....	Pg s372	360100.....	Pg s385
4062.....	Pg s386	337005.....	Pg s383	360110.....	Pg s385
4063.....	Pg s386	337006.....	Pg s378	360120.....	Pg s385
4064.....	Pg s386	337007.....	Pg s383	360130.....	Pg s385
4069.....	Pg s386	337008.....	Pg s383	360140.....	Pg s385
4070.....	Pg s386	338050.....	Pg s381	360160.....	Pg s385
4088.....	Pg s386	338104.....	Pg s380	360172.....	Pg s385
5902.....	Pg s386	338200.....	Pg s380	370040.....	Pg s382
5903.....	Pg s386	339516.....	Pg s374	370041.....	Pg s380
5905.....	Pg s386	340001.....	Pg s378	370044.....	Pg s380
5907.....	Pg s386	340002.....	Pg s378	370045.....	Pg s355
5910.....	Pg s386	340010.....	Pg s379	370046.....	Pg s355
5919.....	Pg s386	340011.....	Pg s379	370050.....	Pg s382
5920.....	Pg s386	340012.....	Pg s379	371024.....	Pg s382
5925.....	Pg s386	340013.....	Pg s379	371025.....	Pg s382
300169.....	Pg s344	340014.....	Pg s379	371042.....	Pg s382
300170.....	Pg s342	340015.....	Pg s379	371045.....	Pg s382
300185.....	Pg s352	340016.....	Pg s379	371070.....	Pg s382
300188.....	Pg s356	340017.....	Pg s379	380020.....	Pg s381
300191.....	Pg s362	350003.....	Pg s378	380910.....	Pg s381
300192.....	Pg s360	350020.....	Pg s378		
300195.....	Pg s346	350110.....	Pg s379		

**KICHLER®**  
World Headquarters  
7711 E. Pleasant Valley Rd.  
PO Box 318010  
Cleveland, Ohio 44131-8010

# CEILING FANS

Featured on front cover:  
Shuriken™ Ceiling Fan 300209  
See pages s338 – s339



GET INSPIRED AT  
[KICHLER.COM](http://KICHLER.COM)

**KICHLER**

*Style to live by™*

Catalog No. **K115**  
[www.kichler.com](http://www.kichler.com)  
Printed in USA  
14-KF-3171-100M  
© Copyright. All rights reserved. Kichler®  
The majority of newer Kichler fixtures  
are U.S. and Canadian Patent Pending.