

**V18**



**WAVE**  
LIGHTING

877.870.WAVE (9283) • [www.wavelighting.com](http://www.wavelighting.com)

# TABLE OF CONTENTS

## VISUAL INDEX

Visual Index	4-5
--------------	-----

## SUSTAINABLE TECHNOLOGY

Eco-Friendly Technologies	6-7
Product Designation Key	7

## MATERIALS

Non-Corrosive Technologies	8
----------------------------	---

## INDOOR LIGHTING

Oceana	10
Vanora	11
Noelani	11
Cascade	12

## ENDURACAST

Villa	14
Cavalier	14
Chateau	15
Citadel	16, 60
Walkway	17, 59

## EVERSTONE™

Companion Size Lanterns	18
Full Size Lanterns	19
Everstone Globes	20
Everstone Acorns	21
Wall Pack Lanterns	21
Turtle Friendly	22

## MARLEX®

Turtle & Dark Sky Friendly	23
Luna	24
Nautical	24-27
Hawthorne	28
Park Point	29
Providence	30
New Town	31
Ashland	32
Brentwood	32
Townhouse	33
Guardian	34-35







# VISUAL INDEX



page 10



page 10



page 11



page 11



page 11



page 12



page 12



page 14



page 14



page 15



page 15



page 15



page 16, 60



page 16, 60



page 16, 60



page 17, 59



page 17, 59



page 18



page 18



page 18



page 19



page 19



page 19



page 20



page 20



page 20



page 21



page 21



page 21



page 22



page 23



page 24



page 24



page 24



page 25



page 25



page 25



page 26



page 26



page 26



page 27



page 27



page 27



page 27



page 28



page 28



page 28



page 29



page 29



page 29



page 29



page 30



page 30



page 30



page 30



page 31



page 31



page 31



page 31



page 32



page 32



page 32



page 32



page 33



page 34



page 34



page 34



page 35



page 35



page 35



page 36



page 36



page 36



page 36



page 36



page 36



page 36

# VISUAL INDEX

**Marlex**



page 37    page 37, 42, 44    page 38, 42, 44    page 38    page 39    page 39, 43, 45    page 40    page 40, 43, 45

**GLOBES & ACORNS**



page 41    page 41, 46    page 41, 46    page 41, 46    page 41, 46

**COMMERCIAL LIGHTING**



page 48    page 48    page 49    page 50    page 51    page 52    page 53, 54

page 55    page 55    page 56    page 56    page 56    page 57    page 57    page 58    page 58

**Lamp Posts & Accessories**




page 62    page 63    page 65    page 66, 67    page 68    page 69    page 69    page 70

**INDUSTRIAL**



page 72    page 73    page 74

**LED RETROFITS**



page 76    page 76    page 77    page 77    page 77    page 77    page 78

**REPLACEMENT PARTS**



page 80    page 80    page 80    page 81    page 81    page 81    page 81













# SUSTAINABLE









Wave Lighting offers a complete line of LED fixture options as shown in the table below. Our line covers everything from 12V landscape, to 120V residential, to multi-volt commercial and industrial. Wave Lighting's LED lights are available in a wide range of color temperatures and wattages. In addition, we offer LED fixtures suitable for Type 3 and Dark Sky applications as well as fixtures with dimmable options. Wave Lighting's LED fixtures are the perfect solution for energy savings, performance and maintenance free operation.

## Residential

PICTURE	SERIES	BASE/TYPE	VOLTAGE	DRIVER	DIMMABLE	LIFE	WARRANTY	CERTS
	LR	Dedicated LED	120V, 50/60 Hz	On-Board	Triac	50,000 L <sub>70</sub>	5 Years	 
	LE26	E26 Medium Base Socket	120V, 50/60 Hz	On-Board	Triac	15,000 L <sub>70</sub>	3 Years	 
	L	Dedicated LED	120-277V, 50/60 Hz	Remote	No	50,000 L <sub>70</sub>	3 Years	 
	LV	Screw Terminal Base	12V, 50/60 Hz	Remote Transformer Not Included	No	50,000 L <sub>70</sub>	3 Years	<b>LOW VOLTAGE SYSTEM</b> <b>N/A</b>

## Commercial

PICTURE	SERIES	BASE/TYPE	VOLTAGE	DRIVER	DIMMABLE	LIFE	WARRANTY	CERTS
	L	Dedicated LED	120-277V, 50/60 Hz	Remote	0-10V	50,000 L <sub>70</sub>	5 Years	 
	LC	E39 Mogul Base Socket	120-277V, 50/60 Hz	On-Board	No	50,000 L <sub>70</sub>	5 Years	 

# TECHNOLOGY



ENERGY STAR® was introduced by the Environmental Protection Agency in 1992 as a voluntary market-based partnership to reduce greenhouse gas emissions through increased energy efficiency. Wave Lighting is an ENERGY STAR® partner committed to improving the energy efficiency of products for homes and businesses. All of our ENERGY STAR® qualified products meet the latest requirements for efficiency. For more information about ENERGY STAR®, visit [www.energystar.gov](http://www.energystar.gov). Look for the ENERGY STAR® icon for compliant products.



Wave Lighting is a proud member of The American Lighting Association (ALA). The ALA is a trade association that represents the lighting industry, their members and customers, and works to protect and advance the industry while promoting the sale and proper application of quality lighting products. It represents 1,500 leading lighting manufacturers, retailers, manufacturers' representatives and designers across North America.



Wave Lighting is proud to offer a wide range of lighting fixtures that meet the Buy American Act (BAA) requirements. The BAA was created to stimulate the economy by specifying how government agencies purchase products. Look for the "Buy American Act Compliant" icon for qualifying fixtures.























Sea turtles are an endangered species. Between March and October, sea turtle hatchlings are confused by the artificial light from coastal dwellings and head toward pools and streets instead of the safety of the sea. Wave Lighting's turtle-friendly lighting directs light to the ground and is not disruptive to the hatchling turtles.



Light pollution from outdoor lighting wastes billions of dollars and vast quantities of natural resources. Our night sky friendly fixtures and retrofits focus light downward reducing light pollution and safeguarding our wildlife in their natural environment. Wave Lighting offers night sky friendly outdoor lighting fixtures and retrofits for residential and commercial lighting applications.

## PRODUCT DESIGNATION KEY

 Energy Star® Models Available	 Meets Buy American Act Requirements	 GU24 Models Available	 LED Models Available	 Occupancy Sensor Option Available
 Dark Sky Friendly Options Available	 Non-Corrosive Oceanside® Approved Models	 H.I.D. Models Available	 Listed for Damp Locations	 Listed for Direct Rain Wet Locations
 Turtle Friendly Models	 Meets Americans with Disabilities Act Requirements	 Meets RoHS Requirements	 UL® Listed Item	 Listed for Wet Locations
 Photocell Option Available	 IP85 Rated Item	 ETL Listed Item	 DLC Listed Item	 Lamp Included



## World Leaders in Non-Corrosive Outdoor Lighting Technologies

**WAVE LIGHTING** strives to exceed customer expectations as the lowest cost provider of residential and commercial lamp posts and outdoor lighting products with a special emphasis on new technologies in non-corrosive, energy efficient outdoor lighting. Our commitment to sustainability drives us to develop new and exciting products that meet today's energy consumption requirements and are built to last.



### INDOOR LIGHTING

Wave Lighting introduces a new line of ENERGY STAR<sup>®</sup> Certified LED indoor fixtures. Indoor Lighting adds a contemporary look to any indoor space without breaking the bank. Wave Lighting's goal is to create a variety of indoor fixtures that reduce carbon footprint, save money, and increase comfort in your home.



### ENDURACAST

Wave Lighting's Enduracast fixtures are constructed of sturdy, high-quality die cast aluminum. Powder coated for maximized protection. Perfect to withstand years of condensation and pollution caused by moisture, chemicals, ultra-violet light and harsh weather conditions.



### EVERSTONE™

EverStone™ is a proprietary compression molded, non-metallic composite material that, when formed into our designs, provides a level of beauty and non-corrosive durability that is unavailable in traditional metallic lighting fixtures.

**"Non-Corrosive Lights that Last."**



### MARLEX<sup>®</sup>

Marlex<sup>®</sup> is a non-metallic, injection molded polymer that offers long term, corrosion-resistant service at a very affordable price. This material is extremely UV stable and is an outstanding alternative to metallic fixtures of all types.



### POST TOP GLOBES & ACORNS

Acrylic offers clarity and performance at an affordable price and is extremely UV resistant. Polycarbonate delivers beauty and durability, with the ability to accommodate higher temperatures and wattages and is extremely impact resistant.



### COMMERCIAL LIGHTING FIXTURES

Wave Lighting proudly offers a wide variety of commercial HID lighting fixtures. All of our fixtures are constructed with the industry's finest Metal Halide or High Pressure Sodium ballasts and may be customized with a vast array of options from our Dark Sky Reflectors, glass refractors, to decorative finials. Wave Lighting's commercial product line provides safety and security for all types of applications including parks, pedestrian walkways, and parking areas.



### RESIDENTIAL AND COMMERCIAL LAMP POSTS

Wave Lighting is the leading supplier of residential and commercial lamp posts and accessories. Our extruded aluminum posts are available in round or fluted and for direct burial or surface mount applications. Post lengths range from 7'-14' with wall thicknesses from 0.05"-0.125". We also offer accessories ranging from traditional ladder rests, photocells, to our new NEC compliant convenience outlet with in-use rain shield.




# ***INDOOR***



- Direct/Indirect Light
- Uplight & Downlight
- Occupancy Sensors



**168FM**  
Standard



**GUIDE: 168FM-LR12C-BN-OS**

ITEM #	LENS	LIGHT SOURCE	COLOR	OPTION	
<b>168FM</b>	White	INCANDESCENT (2) 40W MAX Medium Base	<b>BN</b> -Brushed Nickel	<b>CK</b> -Cable Kit <b>PK</b> -Pendant Kit <b>OS</b> -Occupancy Sensor  (CK & PK can not be combined)	
		<b>LED LIGHT SOURCE</b>			
		120V LIGHTWAVE LED <b>LR15</b> -15W 1400lm <b>LR22</b> -23W 1900lm			CCT <b>C</b> -4K <b>W</b> -3K
		E26 MEDIUM BASE LED <b>2LE26</b> -(2) A19 800lm			

**Title 24 Available**  
(call for details)


SCAN FOR VIDEO



**OPTIONAL MOUNTING KITS**  
Mounting kits ship in separate packaging. Assembly required.

**PENDANT KIT**  
6"/13" Pendant

**CABLE KIT**  
36" Max Cable



**GUIDE: 178FM-LR24W-BN**

ITEM #	LENS	LIGHT SOURCE	COLOR	OPTION
<b>178FM</b>	White	<b>LED LIGHT SOURCE</b>	<b>BN</b> -Brushed Nickel	<b>PK</b> -Pendant Kit
		120V LIGHTWAVE LED <b>LR24</b> -24W 1850lm		



**178FM**  
Low Profile


★ Lamp Included  
Energy Star Qualified Product

SPEC SHEETS AND IES FILES AVAILABLE ONLINE. Specifications subject to change without notice. LED option information on page 6.




## GUIDE: 170FM-LR15W-WH-OS

ITEM #	LENS	LIGHT SOURCE	COLOR	OPTION	
<b>170FM</b>	ACRYLIC White	INCANDESCENT (1) 40W MAX Medium Base	<b>WH</b> -White	<b>OS</b> -Occupancy Sensor	
		<b>LED LIGHT SOURCE</b>			
		120V LIGHTWAVE LED <b>LR12</b> -13W 1000lm <b>LR15</b> -15W 1400lm			CCT <b>C</b> -4K <b>W</b> -3K
		E26 MEDIUM BASE LED <b>LE26</b> -(1) A19 800lm			
<b>172FM</b>	ACRYLIC White	INCANDESCENT (2) 40W MAX Medium Base	<b>WH</b> -White	<b>OS</b> -Occupancy Sensor	
		<b>LED LIGHT SOURCE</b>			
		120V LIGHTWAVE LED <b>LR15</b> -15W 1400lm <b>LR22</b> -23W 1900lm			CCT <b>C</b> -4K <b>W</b> -3K
		E26 MEDIUM BASE LED <b>2LE26</b> -(2) A19 800lm			



**170FM**  
Small



**172FM**  
Large


**Title 24 Available**  
(call for details)

# NOELANI





## GUIDE: 160FM-LR15W-WH-OS

ITEM #	LENS	LIGHT SOURCE	COLOR	OPTION	
<b>160FM</b> <b>161FM</b>	ACRYLIC White	INCANDESCENT (1) 40W MAX Medium Base	<b>WH</b> -White	<b>OS</b> -Occupancy Sensor	
		<b>LED LIGHT SOURCE</b>			
		120V LIGHTWAVE LED <b>LR12</b> -13W 1000lm <b>LR15</b> -15W 1400lm			CCT <b>C</b> -4K <b>W</b> -3K
		E26 MEDIUM BASE LED <b>LE26</b> -(1) A19 800lm			
<b>162FM</b> <b>163FM</b>	ACRYLIC White	INCANDESCENT (2) 40W MAX Medium Base	<b>WH</b> -White	<b>OS</b> -Occupancy Sensor	
		<b>LED LIGHT SOURCE</b>			
		120-277V MULTI-VOLT LED <b>L17</b> -17W 1278lm			CCT 3K
		120V LIGHTWAVE LED <b>LR15</b> -15W 1400lm <b>LR22</b> -23W 1900lm			CCT <b>C</b> -4K <b>W</b> -3K
		E26 MEDIUM BASE LED <b>2LE26</b> -(2) A19 800lm			
		120-277V MULTI-VOLT LED <b>L22</b> -22W 1704lm	CCT 3K		




**160FM**  
Small




**162FM**  
Large

**Title 24 Available**  
(call for details)



**161FM**  
Small




**163FM**  
Large





**173FM**



EXTENDS: 4"  
HCMT: 6 1/2"



**GUIDE: 173FM-L17-BN**

ITEM #	LENS	LIGHT SOURCE	COLOR
<b>173FM</b>	GLASS Frost	<b>LED LIGHT SOURCE</b> 120-277V MULTI-VOLT LED L22-22W 1704lm	<b>BN-Brushed Nickel</b> CCT 3K




**174FM**



**GUIDE: 174FM-L17-BN**

ITEM #	LENS	LIGHT SOURCE	COLOR
<b>174FM</b>	GLASS Frost	<b>LED LIGHT SOURCE</b> 120-277V MULTI-VOLT LED L22-22W 1704lm	<b>BN-Brushed Nickel</b> CCT 3K



EXTENDS: 4"  
HCMT: 8 3/8"



Energy Star Qualified Product

SPEC SHEETS AND IES FILES AVAILABLE ONLINE. Specifications subject to change without notice. LED option information on page 6.

**WAVE LIGHTING • PHONE 877.870.WAVE (9283)**

***OUTDOOR***



# Specification Grade!

- Die-Cast Aluminum
- Extreme Durability
- Powdercoated Finish

Wave Lighting's Enduracast fixtures are constructed of sturdy, high-quality die cast aluminum. Each fixture is powder coated for maximized protection. Perfect to withstand years of condensation and pollution caused by moisture, chemicals, ultra-violet light and harsh weather conditions.

## VILLA

**549S**  
Large

17"

7 3/4"

EXTENDS: 9 1/2"  
H/CTR: 7"  
BACKPLATE: 7" x 4 3/4"

**549V**  
Small

14 5/8"

6 5/8"

EXTENDS: 8 1/4"  
H/CTR: 7"  
BACKPLATE: 7" x 4 3/4"

**GUIDE: 549SF-BZ**

ITEM #	LENS	LIGHT SOURCE	COLOR
<b>549S</b>	GLASS	INCANDESCENT	<b>BZ</b> -Bronze
<b>549V</b>	F-Frosted	(1) 75W MAX Medium Base	
<b>LED LIGHT SOURCE</b>			
		<b>E26 MEDIUM BASE LED</b>	<b>CCT</b>
		<b>2LE26-A19 800lm</b>	<b>C-4K</b>
			<b>W-3K</b>

**Title 24 Available**  
(call for details)

## CAVALIER

**GUIDE: 561FMF-BZ**

ITEM #	LENS	LIGHT SOURCE	COLOR
<b>561FM</b>	GLASS F-Frosted	INCANDESCENT (2) 40W MAX Medium Base	<b>BZ</b> -Bronze
<b>LED LIGHT SOURCE</b>			
		<b>E26 MEDIUM BASE LED</b>	<b>CCT</b>
		<b>2LE26-(2) A19 800lm</b>	<b>C-4K</b>
			<b>W-3K</b>

**Title 24 Available**  
(call for details)

**561FM**


9"

13.5"

**Lamp Included**  
**Energy Star Qualified Product**

SPEC SHEETS AVAILABLE ONLINE. Specifications subject to change without notice. LED option information on page 6.






**544HC**





**544S**



EXTENDS: 13 1/2"  
H/CTR: 4"  
BACKPLATE: 6 1/4" x 10 1/4"



**544T**



**544V**

EXTENDS: 11 1/2"  
H/CTR: 4"  
BACKPLATE: 6 1/4" x 10 1/4"

**GUIDE: 549SF-BZ**

ITEM #	LENS	LIGHT SOURCE	COLOR
544HC	GLASS	INCANDESCENT	<b>BZ</b> -Bronze
544S	F-Frosted	(1) 75W MAX Medium Base	
544T		<b>LED LIGHT SOURCE</b>	
544V		E26 MEDIUM BASE LED LE26-A19 800lm ☆ Energy Star	
		CCT C-4K W-3K	

**Title 24 Available**  
(call for details)

\*Energy Star not available on Post Top Fixtures.


SPEC SHEETS AVAILABLE ONLINE. Specifications subject to change without notice. LED option information on page 6.

**FAX 330.630.1994 • WWW.WAVELIGHTING.COM**

- WALL OR CEILING MOUNT
- INSECT & DUST PROOF
- ENCLOSED & GASKETED
- DIE CAST ALUMINUM
- HOSE DOWN
- IP65 RATED





**166FM**  
Ring



**169FM**  
Eyelid



SCAN FOR VIDEO



**GUIDE: 166FMF-LR15C-BK**


ITEM #	DIFFUSER	LIGHT SOURCE	COLOR	OPTION
<b>166FM</b>	POLYCARBONATE	<b>LED LIGHT SOURCE</b>	<b>BK-Black</b>	<b>O-Occupancy Sensor</b>
<b>169FM</b>	<b>F-Frosted</b>	120V LIGHTWAVE LED <b>LR15-15W 1400lm</b> <b>LR22-23W 1900lm</b>	<b>CCT</b> <b>WH-White</b> <b>C-4K</b> <b>W-3K</b>	

- WALL MOUNT
- INSECT & DUST PROOF
- ENCLOSED & GASKETED
- PHOTOCELL INCLUDED
- HOSE DOWN
- IP65 RATED



**GUIDE: 266FMF-LR12-BZ**

ITEM #	DIFFUSER/HOUSING	LIGHT SOURCE	COLOR
<b>266FM</b>	POLYCARBONATE <b>F-Frosted</b>	<b>LED LIGHT SOURCE</b>	<b>BZ-Bronze</b>
		120V LIGHTWAVE LED <b>LR12-13W 1000lm</b>	<b>CCT</b> <b>C-4K</b>




Energy Star Qualified Product

SPEC SHEETS AVAILABLE ONLINE. Specifications subject to change without notice. LED option information on page 6.

**WAVE LIGHTING • PHONE 877.870.WAVE (9283)**

**502VF**

- DOWNLIGHT
- DIE CAST ALUMINUM



EXTENDS: 5 7/8"  
H/CTR: 2 1/4"  
BACKPLATE: 4 1/2" x 4 1/2"




See Page 23 for Non-Metallic Version

**GUIDE: 502VF-LR11W-BK**

ITEM #	LENS	LIGHT SOURCE	COLOR
502V	GLASS F-Frosted	LED LIGHT SOURCE	
		120V LED LR11-11W, 870lm	CCT C-4K W-3K
			BK-Black BZ-Bronze

**502SF**

- UP & DOWNLIGHT
- DIE CAST ALUMINUM




EXTENDS: 5 7/8"  
H/CTR: 2 1/4"  
BACKPLATE: 4 1/2" x 4 1/2"




**GUIDE: 502SF-LR22W-BK**

ITEM #	LENS	LIGHT SOURCE	COLOR
502S	GLASS F-Frosted	LED LIGHT SOURCE	
		120V LED LR22-22W, 1740lm	CCT C-4K W-3K
			BK-Black BZ-Bronze



**C200BC**



Anchor Bolt M10 x 6.7"  
(3 anchor bolts and template included)



**GUIDE: C200BC-L10C-BK**

ITEM #	LENS	LIGHT SOURCE	COLOR	OPTIONS
C200B	POLYCARB C-Clear	LED LIGHT SOURCE		D-0-10v Dimming
		100-277V MULTI-VOLT L10-10W, 937lm	CCT C-4K	
			BK-Black BZ-Bronze	

## Built From The Inside-Out To Last!



SCAN FOR VIDEO


- Compression Molded
- Non-Corrosive Durability
- Limited Lifetime Warranty
- Non-Metallic Composite Material
- OceanSide® Approved
- Withstand Harsh Weather

## OCEANSIDE® APPROVED




The OceanSide® icon indicates that this product meets an uncompromising set of standards for low-maintenance durability and harsh weather performance.

Our advanced engineering, pleasing designs and leading-edge technologies allow us to eliminate components that can fail due to rust, corrosion or exposure to extreme climates. OceanSide® Approved products are specifically designed from the INSIDE-OUT to meet the rigors of Nature's harshest environment.



**S21SC-GY**


EXTENDS:  
9 1/4"  
H/CTR:  
11"  
BACKPLATE:  
7 1/4" x 5 3/8"



### GUIDE: S21VF-BZ-PC

ITEM #	LENS	LIGHT SOURCE	COLOR	OPTION
<b>S21S</b> <b>S21V</b>	<b>ACRYLIC</b> C-Clear F-Frosted	<b>INCANDESCENT</b> (1) 60W MAX Medium Base	<b>BK-Blackstone</b> <b>WH-Whitestone</b> <b>SN-Sandstone</b> <b>GY-Graystone</b> <b>BZ-Bronzestone</b>	<b>PC-Photocell</b> (only available on S21V)
		<b>LED LIGHT SOURCE</b>		
		120V LIGHTWAVE LED <b>LR12-13W 1000lm</b>	<b>CCT</b> <b>C-4K</b> <b>W-3K</b>	
		E26 MEDIUM BASE LED <b>LE26-A19 800lm</b>		
		* PC only available S21V		

**Title 24 & GU24 Available**  
(call for details)



EXTENDS:  
9 1/4"  
H/CTR:  
3 5/8"  
BACKPLATE:  
7 1/4" x 5 3/8"

**S21VF-BZ**




### GUIDE: S21TC-LR12C-SN

ITEM #	LENS	LIGHT SOURCE	COLOR
<b>S21T</b>	<b>ACRYLIC</b> C-Clear F-Frosted	<b>INCANDESCENT</b> (1) 60W MAX Medium Base	<b>BK-Blackstone</b> <b>WH-Whitestone</b> <b>SN-Sandstone</b> <b>GY-Graystone</b> <b>BZ-Bronzestone</b>
		<b>LED LIGHT SOURCE</b>	
		120V LIGHTWAVE LED <b>LR12-13W 1000lm</b>	<b>CCT</b> <b>C-4K</b> <b>W-3K</b>
		E26 MEDIUM BASE LED <b>LE26-A19 800lm</b>	

**Title 24 & GU24 Available**  
(call for details)

**S21TC-SN**



**Title 24 Available**  
(call for details)

### STONE COLORS



★ Lamp Included  
Energy Star Qualified Product


SPEC SHEETS AND IES FILES AVAILABLE ONLINE. Specifications subject to change without notice. LED option information on page 6.



# FULL SIZE LANTERNS



**S11VL-WH**



## GUIDE: S11VC-LR12W-WH-PC

ITEM #	LENS	LIGHT SOURCE	COLOR	OPTION
<b>S11V</b>	<b>ACRYLIC</b> C-Clear F-Frosted L-Opal	<b>INCANDESCENT</b> (1) 100W MAX Medium Base	<b>BK</b> -Blackstone <b>WH</b> -Whitestone <b>SN</b> -Sandstone <b>GY</b> -Graystone <b>BZ</b> -Bronzestone	<b>PC</b> -Photocell (GU24 & LED only)
		<b>LED LIGHT SOURCE</b>		
		<b>120V LIGHTWAVE LED</b>		
		<b>LR12-13W 1000lm</b>	<b>CCT</b>	
		<b>LR15-15W 1400lm</b>	<b>C-4K</b>	
		<b>E26 MEDIUM BASE LED</b>	<b>W-3K</b>	
		<b>LE26-A19 800lm</b>		

**EXTENDS:** 12 3/4"  
**H/CTR:** 5 1/4"  
**BACKPLATE:** 10 5/8" x 5 1/2"

**Title 24 & GU24 Available**  
(call for details)




## GUIDE: S11SC-LR15C-SN


ITEM #	LENS	LIGHT SOURCE	COLOR
<b>S11S</b>	<b>ACRYLIC</b> C-Clear F-Frosted L-Opal	<b>INCANDESCENT</b> (1) 100W MAX Medium Base	<b>BK</b> -Blackstone <b>WH</b> -Whitestone <b>SN</b> -Sandstone <b>GY</b> -Graystone <b>BZ</b> -Bronzestone
		<b>LED LIGHT SOURCE</b>	
		<b>120V LIGHTWAVE LED</b>	<b>CCT</b>
		<b>LR12-13W 1000lm</b>	<b>C-4K</b>
		<b>LR15-15W 1400lm</b>	<b>W-3K</b>
		<b>E26 MEDIUM BASE LED</b>	
		<b>LE26-A19 800lm</b>	

**EXTENDS:** 12 3/4"  
**H/CTR:** 21 1/4"  
**BACKPLATE:** 10 5/8" x 5 1/2"

**Title 24 & GU24 Available**  
(call for details)



**S11TF-BK**



## GUIDE: S11TC-LR12W-BK

ITEM #	LENS	LIGHT SOURCE	COLOR
<b>S11T</b>	<b>ACRYLIC</b> C-Clear F-Frosted L-Opal	<b>INCANDESCENT</b> (1) 100W MAX Medium Base	<b>BK</b> -Blackstone <b>WH</b> -Whitestone <b>SN</b> -Sandstone <b>GY</b> -Graystone <b>BZ</b> -Bronzestone
		<b>LED LIGHT SOURCE</b>	
		<b>120V LIGHTWAVE LED</b>	<b>CCT</b>
		<b>LR12-13W 1000lm</b>	<b>C-4K</b>
		<b>LR15-15W 1400lm</b>	<b>W-3K</b>
		<b>E26 MEDIUM BASE LED</b>	
		<b>LE26-A19 800lm</b>	

**EXTENDS:** 12 3/4"  
**H/CTR:** 21 1/4"  
**BACKPLATE:** 10 5/8" x 5 1/2"

**Title 24 & GU24 Available**  
(call for details)

Posts accommodate Photo Control 320 or 688. See page 69. Posts sold separately.

SPEC SHEETS AND IES FILES AVAILABLE ONLINE. Specifications subject to change without notice. LED option information on page 6.

**FAX 330.630.1994 • WWW.WAVELIGHTING.COM**




## GUIDE: S26SL-LE26-BK

ITEM #	GLOBE	LIGHT SOURCE	COLOR
<b>S26S</b> <b>S26V</b>	<b>ACRYLIC</b> <b>C</b> -Clear Prismatic <b>L</b> -Opal	<b>INCANDESCENT</b> (1) 60W MAX Medium Base	<b>BK</b> -Blackstone <b>WH</b> -Whitestone <b>SN</b> -Sandstone <b>GY</b> -Graystone <b>BZ</b> -Bronzestone
		<b>LED LIGHT SOURCE</b>	
		<b>E26 MEDIUM BASE LED</b> <b>LE26-A19 800lm</b> ☆	<b>CCT</b> <b>C</b> -4K <b>W</b> -3K




**S26SL-BK**



**EXTENDS:**  
9 1/4"  
**H/CTR:**  
8 3/4"  
**BACKPLATE:**  
7 1/4" x 5 3/8"



**S26VC-SN**




**EXTENDS:**  
9 1/4"  
**H/CTR:**  
3 5/8"  
**BACKPLATE:**  
7 1/4" x 5 3/8"

**Title 24 & GU24 Available**  
(call for details)



**S26TC-WH**



I.D. = 3"



## GUIDE: S26TC-WH

ITEM #	GLOBE	LIGHT SOURCE	COLOR
<b>S26T</b>	<b>ACRYLIC</b> <b>C</b> -Clear Prismatic <b>L</b> -Opal	<b>INCANDESCENT</b> (1) 100W MAX Medium Base	<b>BK</b> -Blackstone <b>WH</b> -Whitestone <b>SN</b> -Sandstone <b>GY</b> -Graystone <b>BZ</b> -Bronzestone
		<b>LED LIGHT SOURCE</b>	
		<b>E26 MEDIUM BASE LED</b> <b>LE26-A19 800lm</b> ☆	<b>CCT</b> <b>C</b> -4K <b>W</b> -3K

**Title 24 & GU24 Available**  
(call for details)

### STONE COLORS



Posts accommodate Photo Control 320 or 688. See page 69. Posts sold separately.

SPEC SHEETS AND IES FILES AVAILABLE ONLINE. Specifications subject to change without notice. LED option information on page 6.

# EVERSTONE ACORNS




## GUIDE: S27SC-BK

ITEM #	GLOBE	LIGHT SOURCE	COLOR
<b>S27SC</b>	POLYCARBONATE Clear Textured	<b>INCANDESCENT</b> (1) 60W MAX Medium Base	<b>BK</b> -Blackstone <b>WH</b> -Whitestone <b>SN</b> -Sandstone <b>GY</b> -Graystone <b>BZ</b> -Bronzestone
		<b>LED LIGHT SOURCE</b>	
		<b>E26 MEDIUM BASE LED</b> <b>LE26-A19 800lm</b> ☆	<b>CCT</b> <b>C-4K</b> <b>W-3K</b>

**Title 24 & GU24 Available**  
(call for details)




## S27SC-BK



**EXTENDS:**  
9 1/4"  
**H/CTR:**  
13 3/4"  
**BACKPLATE:**  
7 1/4" x 5 3/8"



## S27TC-GY



## GUIDE: S27TC-WH

ITEM #	GLOBE	LIGHT SOURCE	COLOR
<b>S27TC</b>	POLYCARBONATE Clear Textured	<b>INCANDESCENT</b> (1) 100W MAX Medium Base	<b>BK</b> -Blackstone <b>WH</b> -Whitestone <b>SN</b> -Sandstone <b>GY</b> -Graystone <b>BZ</b> -Bronzestone
		<b>LED LIGHT SOURCE</b>	
		<b>E26 MEDIUM BASE LED</b> <b>LE26-A19 800lm</b> ☆	<b>CCT</b> <b>C-4K</b> <b>W-3K</b>

**Title 24 & GU24 Available**  
(call for details)

# WALL PACK LANTERNS




## GUIDE: S32WC-LR12C-BK-PC

ITEM #	DIFFUSER	LIGHT SOURCE	COLOR	
<b>S32W</b>	ACRYLIC <b>C</b> -Clear Prismatic <b>L</b> -Opal	<b>INCANDESCENT</b> (1) 60W MAX Medium Base	<b>BK</b> -Blackstone <b>WH</b> -Whitestone <b>SN</b> -Sandstone <b>GY</b> -Graystone <b>BZ</b> -Bronzestone	
		<b>LED LIGHT SOURCE</b>		
		<b>120V LIGHTWAVE LED</b> <b>LR12-13W 1000lm</b>		<b>CCT</b> <b>C-4K</b> <b>W-3K</b>
		<b>E26 MEDIUM BASE LED</b> <b>LE26-A19 800lm</b> ☆		
		<b>120-277V MULTI-VOLT LED</b> <b>L11-11W 912lm</b>	<b>CCT</b> <b>4K</b>	

**Title 24 & GU24 Available**  
(call for details)

## S32WC-BK



**EXTENDS:**  
4"  
**H/CTR:**  
7 1/2"  
**BACKPLATE:**  
13 7/8" x 6 3/4"



☆ **Lamp Included**

**Energy Star Qualified Product**

SPEC SHEETS AND IES FILES AVAILABLE ONLINE. Specifications subject to change without notice. LED option information on page 6.

**FAX 330.630.1994 • WWW.WAVELIGHTING.COM**





**S33WN-SN**



**(N) No Insignia**



**(L) Lighthouse**



**(T) Turtle**




**\*Custom**  
(consult factory for details)

- Florida Wildlife Certified with Amber LED Light Source
- Meets Standards for Beachfront, Turtle Safe Lighting
- 100% Cut-Off - Complies with Dark Sky Standards
- Available with No Insignia, Lighthouse, Turtle, or Custom Insignia
- Non-Corrosive Hardware





**S33WL-L9-SN**



EXTENDS:  
4"  
H/CTR:  
7 3/4"  
BACKPLATE:  
14 1/8" x 6 3/4"

**GUIDE: S33WL-L9-SN-PC**

ITEM #	INSIGNIA	LIGHT SOURCE	COLOR
<b>S33W</b>	<b>N</b> -No Insignia	<b>INCANDESCENT</b> (1) 60W MAX Medium Base	<b>BK</b> -Blackstone
	<b>L</b> -Lighthouse		<b>WH</b> -Whitestone
	<b>T</b> -Turtle		<b>SN</b> -Sandstone
			<b>GY</b> -Graystone
			<b>BZ</b> -Bronzestone
		<b>LED LIGHT SOURCE</b>	
		120V LIGHTWAVE LED	CCT
		<b>LR12-13W 1000lm</b> 	<b>C-4K</b>
		E26 MEDIUM BASE LED	<b>W-3K</b>
		<b>LE26-A19 800lm</b> 	
		120-277V MULTI-VOLT LED	CCT
		<b>L11-11W 912lm</b>	<b>3K</b>
		<b>120-277V AMBER LED</b>	
		<b>L9*-A19 470lm, 585-595nm</b>	

Customizable Insignia Available. Consult factory for details.

**Title 24 & GU24 Available**  
(call for details)



**\*FLORIDA WILDLIFE CERTIFIED LIGHTING**

 **Lamp Included**  
**Energy Star Qualified Product**

SPEC SHEETS AND IES FILES AVAILABLE ONLINE. Specifications subject to change without notice. LED option information on page 6.



# TURTLE & DARK SKY FRIENDLY

Marlex

NON-CORROSIVE

- Available in Two Lengths
- Turtle Safe & Dark Sky Friendly Lighting
- Non-Corrosive Construction
- Baffle Included



## GUIDE: S34W-BK



ITEM #	LIGHT SOURCE	COLOR
<b>S34W</b>	<b>INCANDESCENT</b>	<b>BK-Black</b>
<b>S35W</b>	(1) 75W MAX Par 30 Lamp	<b>WH-White</b>
<b>LED LIGHT SOURCE</b>		
	<b>E26 MEDIUM BASE LED</b>	<b>CCT</b>
	<b>LE26- (1) A19 800lm</b>	<b>C-4K</b>
		<b>W-3K</b>

**Title 24 Available**  
(call for details)



## S35W-WH

Tall



## S34W-BK

Short

**See Page 17 for Cast Aluminum Version!**



## S35W-WH




SPEC SHEETS AND IES FILES AVAILABLE ONLINE. Specifications subject to change without notice. LED option information on page 6.

FAX 330.630.1994 • WWW.WAVELIGHTING.COM

## CEILING MOUNT



**167FM-BK**



### GUIDE: 167FM-WH

ITEM #	DIFFUSER	LIGHT SOURCE	COLOR
<b>167FM</b>	<b>ACRYLIC F-Frosted</b>	<b>INCANDESCENT</b> (1) 75W MAX Medium Base	<b>BK-Black</b> <b>WH-White</b>
		<b>LED LIGHT SOURCE</b>	
		<b>120V LIGHTWAVE LED</b>	<b>CCT</b>
		<b>LR12-13W 1000lm</b>	<b>C-4K</b>
		<b>LR15-15W 1400lm</b>	<b>W-3K</b>
		<b>LR22-23W 1900lm</b>	
		<b>E26 MEDIUM BASE LED</b>	
		<b>LE26 (1) A19 800lm</b>	

**Title 24 & GU24 Available**  
(call for details)

## NAUTICAL




### GUIDE: S759VF-LR12W-BK-PC


ITEM #	DIFFUSER	LIGHT SOURCE	COLOR	OPTION
<b>S759V</b>	<b>ACRYLIC F-Frosted</b>	<b>INCANDESCENT</b> (1) 60W MAX Medium Base	<b>BK-Black</b>	<b>PC-Photocell</b>
		<b>LED LIGHT SOURCE</b>		
		<b>120V LIGHTWAVE LED</b>		<b>CCT</b>
		<b>LR12-13W 1000lm</b>		<b>C-4K</b>
		<b>E26 MEDIUM BASE LED</b>		<b>W-3K</b>
		<b>LE26 (1) A19 800lm</b>		

**Title 24 & GU24 Available**  
(call for details)

**S759VF-BK**



**S75VC-BK**



### GUIDE: S75VC-WH-PC

ITEM #	DIFFUSER	LIGHT SOURCE	COLOR	OPTION
<b>S75V</b>	<b>ACRYLIC C-Clear Prismatic L-Opal</b>	<b>INCANDESCENT</b> (1) 60W MAX Medium Base	<b>BK-Black</b> <b>WH-White</b>	<b>PC-Photocell</b>
		<b>LED LIGHT SOURCE</b>		
		<b>120V LIGHTWAVE LED</b>		<b>CCT</b>
		<b>LR12-13W 1000lm</b>		<b>C-4K</b>
		<b>E26 MEDIUM BASE LED</b>		<b>W-3K</b>
		<b>LE26-A19 800lm</b>		
		<b>120-277V MULTI-VOLT LED</b>		<b>CCT</b>
		<b>L11-11W 912lm</b>		<b>4K</b>



**Title 24 & GU24 Available**  
(call for details)



## GUIDE: S75TC-1-LR12C-WH-PC


ITEM #	DIFFUSER	LIGHT SOURCE	COLOR	OPTION
<b>S75TC-1</b>	<b>ACRYLIC</b> Clear Prismatic	<b>INCANDESCENT</b> (1) 60W MAX Medium Base	<b>BK-Black</b> <b>WH-White</b>	<b>PC-Photocell</b>
<b>S75TL-1</b>	<b>ACRYLIC</b> Opal	<b>LED LIGHT SOURCE</b>		
		<b>120V LIGHTWAVE LED</b> <b>LR12-13W 1000lm</b>	<b>CCT C-4K</b> <b>W-3K</b>	
		<b>E26 MEDIUM BASE LED</b> <b>LE26-A19 800lm</b> ☆		
		<b>120-277V MULTI-VOLT LED</b> <b>L11-11W 912lm</b>	<b>CCT 4K</b>	

**Title 24 & GU24 Available**  
(call for details)



## GUIDE: S75TC-2-WH-PC

ITEM #	DIFFUSER	LIGHT SOURCE	COLOR	OPTION
<b>S75TC-2</b>	<b>ACRYLIC</b> Clear Prismatic	<b>INCANDESCENT</b> (2) 60W MAX Medium Base	<b>BK-Black</b> <b>WH-White</b>	<b>PC-Photocell</b>
<b>S75TL-2</b>	<b>ACRYLIC</b> Opal	<b>LED LIGHT SOURCE</b>		
		<b>120V LIGHTWAVE LED</b> <b>LR12-(2)13W 1000lm</b>	<b>CCT C-4K</b> <b>W-3K</b>	
		<b>E26 MEDIUM BASE LED</b> <b>LE26-(2)A19 800lm</b> ☆		
		<b>120-277V MULTI-VOLT LED</b> <b>L22-22W 1824lm</b>	<b>CCT 4K</b>	



**Title 24 & GU24 Available**  
(call for details)



## GUIDE: S75TC-BK-PC



ITEM #	DIFFUSER	LIGHT SOURCE	COLOR
<b>S75TC</b>	<b>ACRYLIC</b> Clear Prismatic	<b>INCANDESCENT</b> (1) 60W MAX Medium Base	<b>BK-Black</b> <b>WH-White</b>
		<b>LED LIGHT SOURCE</b>	
		<b>120V LIGHTWAVE LED</b> <b>LR12-13W 1000lm</b>	<b>CCT C-4K</b> <b>W-3K</b>
		<b>E26 MEDIUM BASE LED</b> <b>LE26-A19 800lm</b> ☆	

**Title 24 & GU24 Available**  
(call for details)

## S75TC-WH



**Pier Mount Adaptors Available**  
(page 69)



Posts sold separately.

☆ **Lamp Included**  
Energy Star Qualified Product

SPEC SHEETS AND IES FILES AVAILABLE ONLINE. Specifications subject to change without notice. LED option information on page 6.



- WALL OR CEILING MOUNT
- PHOTOCELL ON SELECT MODELS
- STANDARD BULKHEAD DESIGN
- LED OPTIONS AVAILABLE




## GUIDE: S761WF-LR12W-WH-PC

ITEM #	DIFFUSER	LIGHT SOURCE	COLOR	OPTION
S761WF S772WF S791WF	POLYCARBONATE Frosted Ribbed	POLYCARBONATE BACK PAN - MEDIUM BASE SOCKET		
		INCANDESCENT (1) 60W MAX Medium Base	BK-Black WH-White	
		LED LIGHT SOURCE		
E26 MEDIUM BASE LED LE26-A19 800lm	CCT C-4K W-3K			
ALUMINUM BACK PAN - DEDICATED LED				
		LED LIGHT SOURCE		BK-Black WH-White PC-Photocell
120V LIGHTWAVE LED		CCT	C-4K W-3K	
LR12-13W 1000lm				
LR15-15W 1400lm				
LR22-23W 1900lm				
120-277V MULTI-VOLT LED		CCT		
L22-22W 1824lm		4K		


Title 24 & GU24  
Available  
(call for details)





S761WF-WH




S791WF-WH




S772WF-BK



- WALL MOUNT
- STANDARD BULKHEAD DESIGN
- PHOTOCELL ON SELECT MODELS
- LED OPTIONS AVAILABLE




POLYCARBONATE BACK PAN




ALUMINUM BACK PAN



S76WF-WH



POLYCARBONATE BACK PAN



ALUMINUM BACK PAN



S771WF-BK


S77WF-WH




### GUIDE: S76WF-WH-PC

ITEM #	DIFFUSER	LIGHT SOURCE	COLOR	OPTION
S76WF S771WF S77WF S79WF	POLYCARBONATE Frosted Ribbed	<b>POLYCARBONATE BACK PAN - MEDIUM BASE SOCKET</b>		
		<b>INCANDESCENT</b> (1) 60W MAX Medium Base	<b>BK-Black</b> <b>WH-White</b>	
		<b>LED LIGHT SOURCE</b>		
		<b>E26 MEDIUM BASE LED</b> <b>LE26-A19 800lm</b>	<b>CCT</b> <b>C-4K</b> <b>W-3K</b>	
		<b>ALUMINUM BACK PAN - DEDICATED LED</b>		
		<b>LED LIGHT SOURCE</b>		
		<b>120V LIGHTWAVE LED</b> <b>LR12-13W 1000lm</b>	<b>CCT</b> <b>C-4K</b> <b>W-3K</b>	<b>PC-Photocell</b>
		<b>120-277V MULTI-VOLT LED</b> <b>L11-11W 912lm</b>	<b>CCT</b> <b>4K</b>	

**Title 24  
& GU24  
Available**  
(call for details)




POLYCARBONATE BACK PAN




ALUMINUM BACK PAN

S79WF-BK



POLYCARBONATE BACK PAN



ALUMINUM BACK PAN

**ADA NOTE:** Only S79WF with Polycarbonate Back Pan is ADA compliant.


- ★ Lamp Included
- Energy Star Qualified Product

SPEC SHEETS AND IES FILES AVAILABLE ONLINE. Specifications subject to change without notice. LED option information on page 6.

NON-CORROSIVE



## 206VC-WH



EXTENDS: 5 3/4"  
H/CTR: 2 3/8"  
BACKPLATE: 4 7/8" RD.

### GUIDE: 206VC-WH-PC


ITEM #	LENS	LIGHT SOURCE	COLOR	OPTION
206VC	ACRYLIC Clear Glacier	INCANDESCENT (1) 60W MAX Medium Base	BK-Black WH-White	PC-Photocell (GU24 & LED only)
		<b>LED LIGHT SOURCE</b>		
		120V LIGHTWAVE LED LR12-13W 1000lm	CCT C-4K	
		E26 MEDIUM BASE LED LE26-A19 800lm	W-3K	

**Title 24  
& GU24  
Available**  
(call for details)



## 208SL-BK

(Opal Beveled Shown)



EXTENDS:  
8 1/2"  
H/CTR:  
10 5/8"  
BACKPLATE:  
4 5/8" x 4 5/8"

### GUIDE: 208SC-LR12W-BK-PC


ITEM #	LENS	LIGHT SOURCE	COLOR	OPTION
208S	ACRYLIC C-Clear Glacier B-Clear Beveled L-Opal Beveled	INCANDESCENT (1) 60W MAX Medium Base	BK-Black WH-White	PC-Photocell
		<b>LED LIGHT SOURCE</b>		
		120V LIGHTWAVE LED LR12-13W 1000lm	CCT C-4K	
		E26 MEDIUM BASE LED LE26-A19 800lm	W-3K	

**Title 24 & GU24 Available**  
(call for details)



## 208TC-WH

(Clear Glacier Shown)



I.D. = 3"



### GUIDE: 208TC-WH

ITEM #	LENS	LIGHT SOURCE	COLOR
208T	ACRYLIC C-Clear Glacier B-Clear Beveled L-Opal Beveled	INCANDESCENT (1) 60W MAX Medium Base	BK-Black WH-White
		<b>LED LIGHT SOURCE</b>	
		120V LIGHTWAVE LED LR12-13W 1000lm	CCT C-4K
		E26 MEDIUM BASE LED LE26-A19 800lm	W-3K

**Title 24 & GU24 Available**  
(call for details)



Posts accommodate Photo Control 320 or 688. See page 69 Posts sold separately.

SPEC SHEETS AND IES FILES AVAILABLE ONLINE. Specifications subject to change without notice. LED option information on page 6.






## GUIDE: 785-LR12C-BK-PC

ITEM #	DIFFUSER	LIGHT SOURCE	COLOR	OPTION	
785	ACRYLIC Opal	INCANDESCENT (1) 60W MAX Medium Base	BK-Black WH-White	PC-Photocell	
		LED LIGHT SOURCE			
		120V LIGHTWAVE LED LR12-13W 1000lm	CCT C-4K		
		E26 MEDIUM BASE LED LE26-A19 800lm	W-3K		
		120-277V MULTI-VOLT LED L11-11W 912lm	CCT 4K		

**Title 24 & GU24 Available**  
(call for details)



**785-BK**



**204SC-WH**




## GUIDE: 204SC-WH-PC

ITEM #	LENS	LIGHT SOURCE	COLOR	OPTION
204S	ACRYLIC	INCANDESCENT (1) 60W MAX Medium Base	BK-Black WH-White	PC-Photocell
204V	C-Clear Beveled L-Opal Beveled			
		LED LIGHT SOURCE		
		120V LIGHTWAVE LED LR12-13W 1000lm	CCT C-4K	
		E26 MEDIUM BASE LED LE26-A19 800lm	W-3K	

**Title 24 & GU24 Available**  
(call for details)



**204VC-BK**



## GUIDE: 204TC-LR12C-WH

ITEM #	LENS	LIGHT SOURCE	COLOR	
204T	ACRYLIC C-Clear Beveled L-Opal Beveled	INCANDESCENT (1) 60W MAX Medium Base	BK-Black WH-White	
		LED LIGHT SOURCE		
		120V LIGHTWAVE LED LR12-13W 1000lm	CCT C-4K	
		E26 MEDIUM BASE LED LE26-A19 800lm	W-3K	

**Title 24 & GU24 Available**  
(call for details)

**204TC-WH**



★ **Lamp Included**  
★ **Energy Star Qualified Product**

SPEC SHEETS AND IES FILES AVAILABLE ONLINE. Specifications subject to change without notice. LED option information on page 6.


**NON-CORROSIVE**

**270SF-BK**  
(frosted beveled shown)




**GUIDE: 270TC-LR12C-BK**

ITEM #	LENS	LIGHT SOURCE	COLOR
<b>270S</b>	<b>ACRYLIC</b>	<b>INCANDESCENT</b>	<b>BK-Black</b>
<b>270T</b>	<b>C-Clear Beveled w/Glass Chimney</b>	(1) 60W MAX Medium Base	
	<b>F-Frosted Beveled</b>		
		<b>LED LIGHT SOURCE</b>	
		120V LIGHTWAVE LED	CCT
		<b>LR12-13W 1000lm</b>	<b>C-4K</b>
		<b>E26 MEDIUM BASE LED</b>	<b>W-3K</b>
		<b>LE26-A19 800lm</b>	



EXTENDS:  
10 1/4"  
H/CTR:  
15"  
BACKPLATE:  
4 7/8" x 5 3/4"



**Title 24 & GU24 Available**  
(call for details)

\*Energy Star not available on Post Top Fixtures.



**Glass Chimney Included when ordered with Clear Beveled Lens**

**270TC-BK**  
(clear beveled w/glass chimney shown)



**220SL-WH**  
Long & Short Tail Included


EXTENDS:  
9"  
H/CTR:  
11 7/8"  
BACKPLATE:  
4 3/4" x 4 3/4"



**GUIDE: 220SC-LR12-WH-PC**

ITEM #	LENS	LIGHT SOURCE	COLOR	OPTION
<b>220S</b>	<b>ACRYLIC</b>	<b>INCANDESCENT</b>	<b>BK-Black</b> <b>WH-White</b>	<b>PC-Photocell</b>
	<b>C-Clear Beveled</b> <b>L-Opal Beveled</b>	(1) 60W MAX Medium Base		
		<b>LED LIGHT SOURCE</b>		
		120V LIGHTWAVE LED	CCT	
		<b>LR12-13W 1000lm</b>	<b>C-4K</b>	
		<b>E26 MEDIUM BASE LED</b>	<b>W-3K</b>	
		<b>LE26-A19 800lm</b>		

**Title 24 & GU24 Available**  
(call for details)



**GUIDE: 220TC-BK**

ITEM #	LENS	LIGHT SOURCE	COLOR
<b>220T</b>	<b>ACRYLIC</b>	<b>INCANDESCENT</b>	<b>BK-Black</b> <b>WH-White</b>
	<b>C-Clear Beveled</b> <b>L-Opal Beveled</b>	(1) 60W MAX Medium Base	
		<b>LED LIGHT SOURCE</b>	
		120V LIGHTWAVE LED	CCT
		<b>LR12-13W 1000lm</b>	<b>C-4K</b>
		<b>E26 MEDIUM BASE LED</b>	<b>W-3K</b>
		<b>LE26-A19 800lm</b>	

**Title 24 & GU24 Available**  
(call for details)

Posts accommodate Photo Control 320 or 688. See page 69 Posts sold separately.

SPEC SHEETS AND IES FILES AVAILABLE ONLINE. Specifications subject to change without notice. LED option information on page 6.



## GUIDE: 240SL-BK-PC

ITEM #	LENS	LIGHT SOURCE	COLOR	OPTION
240S 240V	ACRYLIC	INCANDESCENT (1) 60W MAX Medium Base	BK-Black WH-White	PC-Photocell
	H-Clear Hatch R-Frosted Hatch			
		<b>LED LIGHT SOURCE</b>		
		120V LIGHTWAVE LED LR12-13W 1000lm	CCT C-4K	<b>Title 24 &amp; GU24 Available</b> (call for details)
		E26 MEDIUM BASE LED LE26-A19 800lm	W-3K	

## 240VH-WH




EXTENDS:  
8 1/2"  
H/CTR:  
2 3/4"  
BACKPLATE:  
5 1/2" RD.



## 240SR-BK

Long & Short Tail Included



EXTENDS:  
8 1/2"  
H/CTR:  
13 1/4"  
BACKPLATE:  
5 1/2" RD.




## GUIDE: 240TR-LR12W-WH

ITEM #	LENS	LIGHT SOURCE	COLOR
240T	ACRYLIC	INCANDESCENT (1) 60W MAX Medium Base	BK-Black WH-White
	H-Clear Hatch R-Frosted Hatch		
		<b>LED LIGHT SOURCE</b>	
		120V LIGHTWAVE LED LR12-13W 1000lm	CCT C-4K
		E26 MEDIUM BASE LED LE26-A19 800lm	W-3K

**Title 24 & GU24 Available**  
(call for details)

## 240TR-WH




## 241VC-BK

## AVAILABLE IN BRONZE



## GUIDE: 241VC-BK

ITEM #	LENS	LIGHT SOURCE	COLOR	OPTION
241V	ACRYLIC	INCANDESCENT (1) 60W MAX Medium Base	BK-Black WH-White BZ-Bronze	PC-Photocell (Lightwave LED only)
	C-Clear F-Frost			
		<b>LED LIGHT SOURCE</b>		
		120V LIGHTWAVE LED LR12-13W 1000lm	CCT C-4K	<b>Title 24 &amp; GU24 Available</b> (call for details)
		E26 MEDIUM BASE LED LE26-A19 800lm	W-3K	



EXTENDS:  
6 3/4"  
H/CTR:  
6 1/2"  
BACKPLATE:  
5 1/2" x 4 7/8"

★ Lamp Included  
Energy Star Qualified Product

SPEC SHEETS AND IES FILES AVAILABLE ONLINE. Specifications subject to change without notice. LED option information on page 6.






## GUIDE: 260SC-LR12W-WH-PC

## 260TC-WH




### 260SC-BK

Long & Short Tail Included




EXTENDS:  
9"  
H/CTR:  
15 5/8"  
BACKPLATE:  
4 3/4" x 7 3/4"



\*Energy Star only available on 260S.

Title 24 & GU24 Available  
(call for details)



ITEM #	LENS	LIGHT SOURCE	COLOR	OPTION
260S	ACRYLIC	INCANDESCENT	BK-Black	PC-Photocell
260T	C-Clear Beveled L-Opal Beveled	(1) 75W MAX Medium Base <b>LED LIGHT SOURCE</b> 120V LIGHTWAVE LED CCT LR12-13W 1000lm C-4K E26 MEDIUM BASE LED W-3K LE26-A19 800lm	WH-White	(wall mount only)

## BRENTWOOD



## GUIDE: 230SC-BK-PC


## 230SC-BK

### 230TC-WH


ITEM #	LENS	LIGHT SOURCE	COLOR	OPTION
230S	ACRYLIC	INCANDESCENT	BK-Black	PC-Photocell
230T	C-Clear Beveled	(1) 60W MAX Medium Base <b>LED LIGHT SOURCE</b> 120V LIGHTWAVE LED CCT LR12-13W 1000lm C-4K E26 MEDIUM BASE LED W-3K LE26-A19 800lm	WH-White	(wall mount only)

\*Energy Star only available on 230S.

Title 24 & GU24 Available  
(call for details)



EXTENDS:  
9"  
H/CTR:  
12 1/4"  
BACKPLATE:  
4 3/4" x 4 3/4"



Long & Short Tail Included



Posts accommodate Photo Control 320 or 688. See page 69. Posts sold separately.

SPEC SHEETS AND IES FILES AVAILABLE ONLINE. Specifications subject to change without notice. LED option information on page 6.

## CEILING MOUNT




### GUIDE: 156FM-LR12C-BK-PC

ITEM #	DIFFUSER	LIGHT SOURCE	COLOR
156FM	POLYPROPYLENE Frosted	<b>POLYCARBONATE BACK PAN - MEDIUM BASE SOCKET</b>	
		INCANDESCENT (1) 60W MAX Medium Base	<b>BK-Black</b> <b>WH-White</b>
		<b>LED LIGHT SOURCE</b>	
		E26 MEDIUM BASE LED <b>LE26-A19 800lm</b> ☆	CCT <b>C-4K</b> <b>W-3K</b>
		<b>ALUMINUM BACK PAN - DEDICATED LED</b>	
		<b>LED LIGHT SOURCE</b>	
		120V LIGHTWAVE LED <b>LR12-13W 1000lm</b> ☆ <b>LR15-15W 1400lm</b> ☆	CCT <b>C-4K</b> <b>W-3K</b>
		120-277V MULTI-VOLT LED <b>L11-11W 912lm</b>	CCT 4K

**Title 24 & GU24 Available**  
(call for details)

**156FM-BK**




### GUIDE: 157FM-WH



**157FM-WH**

**Title 24 & GU24 Available**  
(call for details)



ITEM #	DIFFUSER	LIGHT SOURCE	COLOR	OPTION
157FM	POLYPROPYLENE Frosted	<b>POLYCARBONATE BACK PAN - MEDIUM BASE SOCKET</b>		
		INCANDESCENT (2) 60W MAX Medium Base	<b>BK-Black</b> <b>WH-White</b>	
		<b>LED LIGHT SOURCE</b>		
		E26 MEDIUM BASE LED <b>2LE26-(2)A19 800lm</b> ☆	CCT <b>C-4K</b> <b>W-3K</b>	
		<b>ALUMINUM BACK PAN - DEDICATED LED</b>		
		<b>LED LIGHT SOURCE</b>		
		120V LIGHTWAVE LED <b>LR12-13W 1000lm</b> ☆ <b>LR15-15W 1400lm</b> ☆ <b>LR22-23W 1900lm</b> ☆	CCT <b>C-4K</b> <b>W-3K</b>	<b>BK-Black</b> <b>WH-White</b>
		120-277V MULTI-VOLT LED <b>L22-22W 1824lm</b>	CCT 4K	

☆ **Lamp Included**  
Energy Star Qualified Product

SPEC SHEETS AND IES FILES AVAILABLE ONLINE. Specifications subject to change without notice. LED option information on page 6.


- WALL OR CEILING MOUNT
- VANDAL & INSECT RESISTANT
- LED OPTIONS
- KNOCKOUTS FOR CONDUIT
- POLYCARBONATE BASE & DIFFUSER
- OCCUPANCY SENSOR AVAILABLE

## 164FM-BK




### GUIDE: 164FM-BK-O

ITEM #	DIFFUSER	LIGHT SOURCE	COLOR	OPTION													
<b>164FM</b>	POLYCARBONATE	<b>LED LIGHT SOURCE</b>	<b>BK-Black</b>	<b>O-Occupancy Sensor</b>													
<b>165FM</b>	Opal F-Frosted Prismatic	<table border="1"> <tr> <td>120V LIGHTWAVE LED</td> <td>CCT</td> </tr> <tr> <td><b>LR12-13W 1000lm</b></td> <td><b>C-4K</b></td> </tr> <tr> <td><b>LR15-15W 1400lm</b></td> <td><b>W-3K</b></td> </tr> <tr> <td colspan="2">E26 MEDIUM BASE LED</td> </tr> <tr> <td><b>2LE26-A19 800lm</b> ☆</td> <td></td> </tr> <tr> <td>120-277V MULTI-VOLT LED</td> <td>CCT</td> </tr> <tr> <td><b>L22-22W 1824lm</b></td> <td><b>4K</b></td> </tr> </table>	120V LIGHTWAVE LED	CCT	<b>LR12-13W 1000lm</b>	<b>C-4K</b>	<b>LR15-15W 1400lm</b>	<b>W-3K</b>	E26 MEDIUM BASE LED		<b>2LE26-A19 800lm</b> ☆		120-277V MULTI-VOLT LED	CCT	<b>L22-22W 1824lm</b>	<b>4K</b>	<b>WH-White</b>  <b>Title 24 &amp; GU24 Available</b> (call for details)
120V LIGHTWAVE LED	CCT																
<b>LR12-13W 1000lm</b>	<b>C-4K</b>																
<b>LR15-15W 1400lm</b>	<b>W-3K</b>																
E26 MEDIUM BASE LED																	
<b>2LE26-A19 800lm</b> ☆																	
120-277V MULTI-VOLT LED	CCT																
<b>L22-22W 1824lm</b>	<b>4K</b>																




## 165FM-WH



## 15RP2-WH



(lamps not included)



EXTENDS: 6"

H/CTR: 2 1/2"

BACKPLATE: 9" x 5"



### GUIDE: 15RP2-WH



ITEM #	LIGHT SOURCE	COLOR
<b>15RP2</b>	INCANDESCENT (2) 150W MAX Par 38 Lamps	<b>WH-White</b>



- WALL OR CEILING MOUNT
- LED OPTIONS



**263FMF-WH**



**265FMF-WH**




**GUIDE: 263FM-LR12-WH**

ITEM #	DIFFUSER	LIGHT SOURCE	COLOR
<b>263FM</b>	<b>ACRYLIC</b>	<b>INCANDESCENT</b>	<b>WH-White</b>
<b>264FM</b>	<b>F-Frosted Prismatic</b>	(1) 40W MAX Medium Base	
		<b>LED LIGHT SOURCE</b>	
		<b>120V LIGHTWAVE LED</b>	<b>CCT</b>
		<b>LR12-13W 1000lm</b>	<b>C-4K</b>
		<b>E26 MEDIUM BASE LED</b>	<b>W-3K</b>
		<b>LE26-A19 800lm</b>	

**Title 24 Available**  
(call for details)



**264FMF-WH**



**GUIDE: 265FM-LR12-WH-O**


ITEM #	DIFFUSER	LIGHT SOURCE	COLOR	OPTION
<b>265FM</b>	<b>ACRYLIC</b>	<b>INCANDESCENT</b>	<b>WH-White</b>	<b>O-Occupancy Sensor</b>
	<b>F-Frosted Prismatic</b>	(2) 40W MAX Medium Base		
		<b>LED LIGHT SOURCE</b>		
		<b>120V LIGHTWAVE LED</b>	<b>CCT</b>	
		<b>LR15-15W 1400lm</b>	<b>C-4K</b>	
		<b>LR22-23W 1900lm</b>	<b>W-3K</b>	
		<b>E26 MEDIUM BASE LED</b>		
		<b>2LE26-(2) A19 800lm</b>		

**Title 24 Available**  
(call for details)

- ★ Lamp Included
- Energy Star Qualified Product

SPEC SHEETS AND IES FILES AVAILABLE ONLINE. Specifications subject to change without notice. LED option information on page 6.


**209-WH**



**210-BK**



**211-BK-PC**



EXTENDS:  
6 1/2"  
H/CTR:  
2 3/8"  
BACKPLATE:  
4 3/4" x 4 1/2"

**212-WH**



**GUIDE: 209-WH-LR12W-PC**

ITEM #	GLOBE/JAR	COLOR	LIGHT SOURCE	OPTION
<b>209</b>	ACRYLIC Clear Prism	<b>BK</b> -Black	INCANDESCENT (1) 60W MAX Medium Base	<b>PC</b> -Photocell
<b>211</b>		<b>WH</b> -White		
<b>216</b>			<b>LED LIGHT SOURCE</b>	
<b>210</b>	ACRYLIC Opal		120V LIGHTWAVE LED	CCT
<b>212</b>			LR12-13W 1000lm	<b>C-4K</b>
<b>217</b>			E26 MEDIUM BASE LED	<b>W-3K</b>
<b>215</b>	POLYCARBONATE Clear Ribbed		120-277V MULTI-VOLT LED L11-11W 912lm	CCT 4K

Title 24 & GU24 Available  
(call for details)


**216-WH**




**217-BK**



**215-BK**




EXTENDS:  
7 1/4"  
H/CTR:  
2 3/8"  
BACKPLATE:  
4 3/4" x 4 1/2"



EXTENDS:  
9 1/2"  
H/CTR:  
2 3/8"  
BACKPLATE:  
4 3/4" x 4 1/2"

**420L-BK**



**GUIDE: 420-BK-PC**


ITEM #	DIFFUSER	COLOR	LIGHT SOURCE	OPTION
<b>420</b>	ACRYLIC	<b>BK</b> -Black	INCANDESCENT (1) 60W MAX Medium Base	<b>PC</b> -Photocell
<b>421</b>	<b>C</b> -Clear	<b>WH</b> -White		
<b>422</b>	Prismatic L-Opal		<b>LED LIGHT SOURCE</b>	
			E26 MEDIUM BASE LED	CCT
			LE26-A19 800lm	<b>C-4K</b> <b>W-3K</b>

Title 24 & GU24 Available  
(call for details)


★ Lamp Included  
Energy Star Qualified Product



**421C-WH**



**422C-BK**




SPEC SHEETS AND IES FILES AVAILABLE ONLINE. Specifications subject to change without notice. LED option information on page 6.



**GUIDE: 106C-LR12C-PC**



**106**  
Long & Short Tail  
Included




ITEM #	LENS	LIGHT SOURCE	OPTION
105-White 106-Black	ACRYLIC Clear Beveled A-Amber Beveled Diamond C-Clear Beveled Diamond F-Frosted Beveled	INCANDESCENT (1) 60W MAX Medium Base	PC-Photocell (GU24 & LED only)
<b>LED LIGHT SOURCE</b>			
		120V LIGHTWAVE LED LR12-13W 1000lm E26 MEDIUM BASE LED LE26-A19 800lm	CCT C-4K W-3K
<b>Title 24 &amp; GU24 Available</b> (call for details)			

EXTENDS:  
9 3/4"  
H/CTR:  
11 1/2"  
BACKPLATE:  
5 1/2" x 5"



**GUIDE: 109F-LR12W**



**109F**



ITEM #	LENS	LIGHT SOURCE
109-White 110-Black	ACRYLIC Clear Beveled A-Amber Beveled Diamond C-Clear Beveled Diamond F-Frosted Beveled	INCANDESCENT (1) 75W MAX Medium Base
<b>LED LIGHT SOURCE</b>		
		120V LIGHTWAVE LED LR12-13W 1000lm LR15-15W 1400lm E26 MEDIUM BASE LED LE26-A19 800lm
		CCT C-4K W-3K
<b>SEE PAGE 44 FOR HIGH WATTAGE LIGHT COMMERCIAL MODELS</b>		
<b>Title 24 &amp; GU24 Available</b> (call for details)		




**GUIDE: 112-LR15W**



**Glass Chimney  
Included**

**112**



ITEM #	LENS	LIGHT SOURCE
111-White 112-Black	ACRYLIC Clear Beveled A-Amber Beveled Diamond C-Clear Beveled Diamond F-Frosted Beveled	INCANDESCENT (1) 75W MAX Medium Base
<b>LED LIGHT SOURCE</b>		
		120V LIGHTWAVE LED LR12-13W 1000lm LR15-15W 1400lm E26 MEDIUM BASE LED LE26-A19 800lm
		CCT C-4K W-3K
<b>Title 24 &amp; GU24 Available</b> (call for details)		



Posts accommodate Photo Control 320 or 688. See page 69. Posts sold separately.

SPEC SHEETS AND IES FILES AVAILABLE ONLINE. Specifications subject to change without notice. LED option information on page 6.






### GUIDE: 114-LR12W

ITEM #	LENS	LIGHT SOURCE
113-White 114-Black	ACRYLIC Clear Beveled A-Amber Beveled Diamond C-Clear Beveled Diamond F-Frosted Beveled	INCANDESCENT (1) 75W MAX Medium Base
		<b>LED LIGHT SOURCE</b>
		120V LIGHTWAVE LED LR12-13W 1000lm LR15-15W 1400lm E26 MEDIUM BASE LED LE26-A19 800lm ☆
		CCT C-4K W-3K
<b>GU24 Available</b> (call for details)		




114



Glass Chimney  
Included



115C



### GUIDE: 115C-LR15C

ITEM #	LENS	LIGHT SOURCE
115-White 116-Black	ACRYLIC Clear Beveled A-Amber Beveled Diamond C-Clear Beveled Diamond F-Frosted Beveled	INCANDESCENT (1) 75W MAX Medium Base
		<b>LED LIGHT SOURCE</b>
		120V LIGHTWAVE LED LR12-13W 1000lm LR15-15W 1400lm E26 MEDIUM BASE LED LE26-A19 800lm ☆
		CCT C-4K W-3K
<b>GU24 Available</b> (call for details)		

SEE PAGE 44 FOR  
HIGH WATTAGE  
LIGHT COMMERCIAL  
MODELS

**GU24 Available**  
(call for details)

## VICTORIAN



### GUIDE: 123-LR15C

ITEM #	LENS	LIGHT SOURCE
123-White 124-Black	ACRYLIC Clear	INCANDESCENT (1) 75W MAX Medium Base
		<b>LED LIGHT SOURCE</b>
		120V LIGHTWAVE LED LR12-13W 1000lm LR15-15W 1400lm E26 MEDIUM BASE LED LE26-A19 800lm ☆
		CCT C-4K W-3K
<b>GU24 Available</b> (call for details)		

☆ Lamp Included



124

123


Glass Chimney  
Included

SPEC SHEETS AND IES FILES AVAILABLE ONLINE. Specifications subject to change without notice. LED option information on page 6.




**408**  
Long & Short Tail  
Included

EXTENDS:  
9 3/8"  
H/CTR:  
12 1/4"  
BACKPLATE:  
5 1/2" x 5"



18 1/4"

8"



13 3/4"

8"



**GUIDE: 408-PC**

ITEM #	LENS	LIGHT SOURCE	OPTION
407-White 408-Black	ACRYLIC Clear Beveled A-Amber Beveled Diamond C-Clear Beveled Diamond F-Frosted Beveled	INCANDESCENT (1) 60W MAX Medium Base	PC-Photocell (GU24 & LED only)
<b>LED LIGHT SOURCE</b>			
		120V LIGHTWAVE LED LR12-13W 1000lm E26 MEDIUM BASE LED LE26-A19 800lm	CCT C-4K W-3K

**GU24 Available**  
(call for details)




**GUIDE: 410F-LR12C**

ITEM #	LENS	LIGHT SOURCE
409-White 410-Black	ACRYLIC Clear Beveled A-Amber Beveled Diamond C-Clear Beveled Diamond F-Frosted Beveled	INCANDESCENT (1) 75W MAX Medium Base
<b>LED LIGHT SOURCE</b>		
		120V LIGHTWAVE LED LR12-13W 1000lm LR15-15W 1400lm E26 MEDIUM BASE LED LE26-A19 800lm

SEE PAGE 44 FOR  
HIGH WATTAGE  
LIGHT COMMERCIAL  
MODELS

**GU24 Available**  
(call for details)




I.D. = 3"

**410F**



**412**

Glass Chimney  
Included



I.D. = 3"



**GUIDE: 412-LR15W**

ITEM #	LENS	LIGHT SOURCE
411-White 412-Black	ACRYLIC Clear Beveled A-Amber Beveled Diamond C-Clear Beveled Diamond F-Frosted Beveled	INCANDESCENT (1) 75W MAX Medium Base
<b>LED LIGHT SOURCE</b>		
		120V LIGHTWAVE LED LR12-13W 1000lm LR15-15W 1400lm E26 MEDIUM BASE LED LE26-A19 800lm

**GU24 Available**  
(call for details)



Posts accommodate Photo Control 320 or 688. See page 69. Posts sold separately.

SPEC SHEETS AND IES FILES AVAILABLE ONLINE. Specifications subject to change without notice. LED option information on page 6.

NON-CORROSIVE




## GUIDE: 608C-PC


ITEM #	LENS	LIGHT SOURCE	OPTION
607-White	ACRYLIC	INCANDESCENT	PC-Photocell
608-Black	Clear Beveled	(1) 60W MAX Medium Base	(GU24 & LED only)
	A-Amber Beveled Diamond		
	C-Clear Beveled Diamond		
	F-Frosted Beveled		
		<b>LED LIGHT SOURCE</b>	
		120V LIGHTWAVE LED	CCT
		LR12-13W 1000lm	C-4K
		E26 MEDIUM BASE LED	W-3K
		LE26-A19 800lm	

**GU24 Available**  
(call for details)

## 608C Long & Short Tail Included



## 609C



## GUIDE: 609C-LR12C

ITEM #	LENS	LIGHT SOURCE	
609-White	ACRYLIC	INCANDESCENT	
610-Black	Clear Beveled	(1) 75W MAX Medium Base	
	A-Amber Beveled Diamond		
	C-Clear Beveled Diamond		
	F-Frosted Beveled		
		<b>LED LIGHT SOURCE</b>	
		120V LIGHTWAVE LED	CCT
		LR12-13W 1000lm	C-4K
		LR15-15W 1400lm	W-3K
		E26 MEDIUM BASE LED	
		LE26-A19 800lm	

SEE PAGE 45 FOR HIGH WATTAGE  
LIGHT COMMERCIAL MODELS

**GU24 Available**  
(call for details)




## GUIDE: 612-LR12C

ITEM #	LENS	LIGHT SOURCE	
611-White	ACRYLIC	INCANDESCENT	
612-Black	Clear Beveled	(1) 75W MAX Medium Base	
	A-Amber Beveled Diamond		
	C-Clear Beveled Diamond		
	F-Frosted Beveled		
		<b>LED LIGHT SOURCE</b>	
		120V LIGHTWAVE LED	CCT
		LR12-13W 1000lm	C-4K
		LR15-15W 1400lm	W-3K
		E26 MEDIUM BASE LED	
		LE26-A19 800lm	

**GU24 Available**  
(call for details)

## 612



**Glass Chimney  
Included**



★ Lamp Included  
Energy Star Qualified Product

SPEC SHEETS AND IES FILES AVAILABLE ONLINE. Specifications subject to change without notice. LED option information on page 6.

WAVE LIGHTING • PHONE 877.870.WAVE (9283)



## COMPLETE GLOBE FIXTURE WITH FITTER FOR 3" POST

- Cast Aluminum or Polycarbonate Fitters
- Polycarbonate or Acrylic Globes



### GUIDE: 2002SM-LE26W-WH

ITEM #	GLOBE	LIGHT SOURCE	FITTER MATERIAL
2001*-12" DIA	POLYCARBONATE Opal <b>CL</b> -Clear <b>SM</b> -Smoke <b>PR</b> -Clear Prismatic	INCANDESCENT See "INCANDESCENT MAX WATTAGES" table for info	POWDERCOATED CAST ALUMINUM Black <b>BZ</b> -Bronze <b>WH</b> -White
2002*-14" DIA			
2003*-16" DIA		LED LIGHT SOURCE	POLYCARBONATE <b>BP</b> -Black <b>WP</b> -White
2004-18" DIA			
8000-10" DIA	ACRYLIC Opal <b>CL</b> -Clear <b>SM</b> -Smoke <b>PR</b> -Clear Prismatic	E26 MEDIUM BASE LED	CCT
8001-12" DIA		LE26-A19 800lm ☆	C-4K
8002*-14" DIA			W-3K
8003-16" DIA			
8004-18" DIA			

\*Not available in Clear Prismatic

ADD MG FOR MOGUL BASE  
SEE PAGE 46 FOR HIGH WATTAGE LIGHT COMMERCIAL MODELS





FITTER I.D. = 3"

RECOMMENDED EQUIVALENT INCANDESCENT MAX WATTAGES		
DIA	POLYCARBONATE	ACRYLIC
10"	-	75W
12"	100W	100W
14"	150W	150W
16"	150W	150W
18"	150W	150W

## COMPLETE ACORN FIXTURE WITH FITTER FOR 3" POST

- Cast Aluminum or Polycarbonate Fitters
- Polycarbonate, Acrylic, or Polyethylene Acorns

8017FA



2018CL



### GUIDE: 2017CL-LR12C-BP

ITEM #	GLOBE/JAR	LIGHT SOURCE	FITTER MATERIAL
2017	POLYCARBONATE <b>CL</b> -Clear Textured	INCANDESCENT (1) 150W MAX Medium Base	POWDERCOATED CAST ALUMINUM Black <b>BZ</b> -Bronze <b>WH</b> -White
2018			
8017	ACRYLIC <b>CL</b> -Clear Textured <b>FA</b> -Frost Textured	LED LIGHT SOURCE	
8018		120V LIGHTWAVE LED	CCT
		LR12- 13W 1000lm LR15- 15W 1400lm LR22- 22W 1800	C-4K W-3K
9017	POLYETHYLENE Opal Textured	E26 MEDIUM BASE LED	
9018		LE26-A19 800lm ☆	

ADD MG FOR MOGUL BASE  
SEE PAGE 46 FOR HIGH WATTAGE LIGHT COMMERCIAL MODELS

Acorns & Globes have  
5 1/4" Neckless Opening  
See Page 80 for Replacements



Posts accommodate Photo Control 320 or 688.  
See page 69. Posts sold separately.

☆ Lamp Included

SPEC SHEETS AND IES FILES AVAILABLE ONLINE. Specifications subject to change without notice. LED option information on page 6.

FAX 330.630.1994 • WWW.WAVELIGHTING.COM


## LOW VOLTAGE LED NON-CORROSIVE POST TOP LANTERNS

- 12V PAR 36 LED Lamp
- 50W Halogen Equivalent
- Estimated 50,000 hrs L<sub>70</sub>
- Maintenance Free Non-Corrosive Housing
- Fits Most 3" O.D. Posts
- Use With 12V Transformers
- Screw Terminal Base Lamp Included
- 10' SPT-2 Wire Included
- 3 Year Warranty

### COLONIAL



**110F**




#### GUIDE: 110C-LV8W

ITEM #	LENS	LIGHT SOURCE	
109-White	ACRYLIC	LED LIGHT SOURCE	
110-Black	Clear Beveled	PAR 36 LED 8-14VAC	CCT
115-White	A-Amber Beveled Diamond	LV8-8W 500lm ☆	W-3K
116-Black	C-Clear Beveled Diamond		
	F-Frosted Beveled		



**115F**




SPEC SHEETS AND IES FILES AVAILABLE ONLINE. Specifications subject to change without notice. LED option information on page 6.

**WAVE LIGHTING • PHONE 877.870.WAVE (9283)**



**610F**



**GUIDE: 610C-LV8W**



ITEM #	LENS	LIGHT SOURCE	
<b>609</b> -White <b>610</b> -Black	<b>ACRYLIC</b> Clear Beveled <b>A</b> -Amber Beveled Diamond <b>C</b> -Clear Beveled Diamond <b>F</b> -Frosted Beveled	<b>LED LIGHT SOURCE</b>	
		<b>PAR 36 LED 8-14VAC</b> <b>LV8-8W 500lm</b> ☆	<b>CCT</b> <b>W-3K</b>

## SAXONY




**409F**



**GUIDE: 410C-LV8W**

ITEM #	LENS	LIGHT SOURCE	
<b>409</b> -White <b>410</b> -Black	<b>ACRYLIC</b> Clear Beveled <b>A</b> -Amber Beveled Diamond <b>C</b> -Clear Beveled Diamond <b>F</b> -Frosted Beveled	<b>LED LIGHT SOURCE</b>	
		<b>PAR 36 LED 8-14VAC</b> <b>LV8-8W 500lm</b> ☆	<b>CCT</b> <b>W-3K</b>



☆ **Lamp Included**

SPEC SHEETS AND IES FILES AVAILABLE ONLINE. Specifications subject to change without notice. LED option information on page 6.

**FAX 330.630.1994 • WWW.WAVELIGHTING.COM**




### LED, METAL HALIDE, & HIGH PRESSURE SODIUM NON-CORROSIVE POST TOP LANTERNS

- Fits Most 3" O.D. Posts
- Maintenance Free Non-Corrosive Housing
- DLC Listed LED Lamp Option
- Lamp Included
- Made in the USA

## COLONIAL



**110C-70H**




#### GUIDE: 110C-70H

ITEM #	LENS	LIGHT SOURCE
109-White 110-Black	ACRYLIC Clear Beveled	<b>INTEGRAL BALLAST</b> <b>METAL HALIDE ELECTRONIC, UNIVERSAL</b> 120-277V HPF
115-White 116-Black	A-Amber Beveled Diamond C-Clear Beveled Diamond F-Frosted Beveled	<b>50MH</b> -(1) 50W 4Kv Medium Base ☆ <b>70MH</b> -(1) 70W 4Kv Medium Base ☆
		<b>HIGH PRESSURE SODIUM</b> <b>MAGNETIC, 120V HPF</b>
		<b>35H</b> -(1) 35W 4Kv Medium Base ☆ <b>50H</b> -(1) 50W 4Kv Medium Base ☆ <b>70H</b> -(1) 70W 4Kv Medium Base ☆
		<b>LED LIGHT SOURCE</b>
		<b>E39 MOGUL BASE CORN COB 100-277v</b> CCT <b>C-4K</b>
		<b>LC5*</b> -24W 3120lm, Type 5 ☆ <b>LC3*</b> -20W 3000lm, Type 3 ☆ <b>LCD*</b> -24W 2400lm, Dark Sky ☆

\*DLC Listed Lamp


**115C-50MH**



Posts accommodate Photo Control 320 or 688. See page 69. Posts sold separately.

SPEC SHEETS AND IES FILES AVAILABLE ONLINE. Specifications subject to change without notice. LED option information on page 6.

WAVE LIGHTING • PHONE 877.870.WAVE (9283)



## GUIDE: 610C-70H



ITEM #	LENS	LIGHT SOURCE
<b>609</b> -White <b>610</b> -Black	<b>ACRYLIC</b> Clear Beveled <b>A</b> -Amber Beveled Diamond <b>C</b> -Clear Beveled Diamond <b>F</b> -Frosted Beveled	<b>INTEGRAL BALLAST</b> <b>METAL HALIDE ELECTRONIC, UNIVERSAL</b> 120-277V HPF <b>50MH</b> -(1) 50W 4Kv Medium Base ☆ <b>70MH</b> -(1) 70W 4Kv Medium Base ☆ <b>HIGH PRESSURE SODIUM</b> <b>MAGNETIC, 120V HPF</b> <b>35H</b> -(1) 35W 4Kv Medium Base ☆ <b>50H</b> -(1) 50W 4Kv Medium Base ☆ <b>70H</b> -(1) 70W 4Kv Medium Base ☆
<b>LED LIGHT SOURCE</b>		
<b>E39 MOGUL BASE CORN COB 100-277v CCT</b>		
<b>LC5</b> *-24W 3120lm, Type 5 ☆		<b>CCT</b> <b>C-4K</b>
<b>LC3</b> *-20W 3000lm, Type 3 ☆		
<b>LCD</b> *-24W 2400lm, Dark Sky ☆		

\*DLC Listed Lamp


# SAXONY

## GUIDE: 410C-70H



ITEM #	LENS	LIGHT SOURCE
<b>409</b> -White <b>410</b> -Black	<b>ACRYLIC</b> Clear Beveled <b>A</b> -Amber Beveled Diamond <b>C</b> -Clear Beveled Diamond <b>F</b> -Frosted Beveled	<b>INTEGRAL BALLAST</b> <b>METAL HALIDE ELECTRONIC, UNIVERSAL</b> 120-277V HPF <b>50MH</b> -(1) 50W 4Kv Medium Base ☆ <b>70MH</b> -(1) 70W 4Kv Medium Base ☆ <b>HIGH PRESSURE SODIUM</b> <b>MAGNETIC, 120V HPF</b> <b>35H</b> -(1) 35W 4Kv Medium Base ☆ <b>50H</b> -(1) 50W 4Kv Medium Base ☆ <b>70H</b> -(1) 70W 4Kv Medium Base ☆
<b>LED LIGHT SOURCE</b>		
<b>E39 MOGUL BASE CORN COB 100-277v CCT</b>		
<b>LC5</b> *-24W 3120lm, Type 5 ☆		<b>CCT</b> <b>C-4K</b>
<b>LC3</b> *-20W 3000lm, Type 3 ☆		
<b>LCD</b> *-24W 2400lm, Dark Sky ☆		

\*DLC Listed Lamp



☆ **Lamp Included**

SPEC SHEETS AND IES FILES AVAILABLE ONLINE. Specifications subject to change without notice. LED option information on page 6.



**COMPLETE GLOBE FIXTURE WITH ALUMINUM FITTER FOR 3" POST**

**GUIDE: 8003SM-70H**

ITEM #	GLOBE	LIGHT SOURCE	FITTER
2003*-16" DIA 2004-18" DIA	<b>POLYCARBONATE</b> Opal <b>CL</b> -Clear <b>SM</b> -Smoke <b>PR</b> -Clear Prismatic	<b>INTEGRAL BALLAST</b> <b>METAL HALIDE ELECTRONIC, UNIVERSAL 120-277V HPF</b> <b>50MH</b> -(1) 50W 4Kv Medium Base ☆ <b>70MH</b> -(1) 70W 4Kv Medium Base ☆	<b>POWDERCOATED CAST ALUMINUM</b> Black <b>BZ</b> -Bronze <b>WH</b> -White
8003-16" DIA 8004-18" DIA	<b>ACRYLIC</b> Opal <b>CL</b> -Clear <b>SM</b> -Smoke <b>PR</b> -Clear Prismatic	<b>HIGH PRESSURE SODIUM MAGNETIC, 120V HPF</b> <b>35H</b> -(1) 35W 4Kv Medium Base ☆ <b>50H</b> -(1) 50W 4Kv Medium Base ☆ <b>70H</b> -(1) 70W 4Kv Medium Base ☆	
		<b>LED LIGHT SOURCE</b>	
		<b>E39 CORN COB LED 100-277v</b> <b>LC5</b> -24W 3120lm, Type 5 ☆ <b>LC3</b> -20W 3000lm, Type 3 ☆ <b>LCD</b> -24W 2400lm, Dark Sky ☆	<b>CCT</b> <b>C-4K</b>

\*Not available in Clear Prismatic

**2003**

2 x 2003 Fixtures with  
**PB5-2** Post Bracket Kit shown below.  
See page 70 for details.



Globes have 5 1/4" Neckless Opening. See Page 80 for Replacements


**COMPLETE ACORN FIXTURE WITH ALUMINUM FITTER FOR 3" POST**



**GUIDE: 2017CL-50MH**

ITEM #	ACORN	LIGHT SOURCE	FITTER
2017 2018	<b>POLYCARBONATE</b> <b>CL</b> -Clear Textured	<b>INTEGRAL BALLAST</b> <b>METAL HALIDE ELECTRONIC, UNIVERSAL 120-277V HPF</b> <b>50MH</b> -(1) 50W 4Kv Medium Base ☆ <b>70MH</b> -(1) 70W 4Kv Medium Base ☆	<b>POWDERCOATED CAST ALUMINUM</b> Black <b>BZ</b> -Bronze <b>WH</b> -White
8017 8018	<b>ACRYLIC</b> <b>CL</b> -Clear Textured <b>FR</b> -Frost Textured	<b>HIGH PRESSURE SODIUM MAGNETIC, 120V HPF</b> <b>35H</b> -(1) 35W 4Kv Medium Base ☆ <b>50H</b> -(1) 50W 4Kv Medium Base ☆ <b>70H</b> -(1) 70W 4Kv Medium Base ☆	
		<b>LED LIGHT SOURCE</b>	
		<b>E39 CORN COB LED 100-277v</b> <b>LC5</b> -24W 3120lm, Type 5 ☆ <b>LC3</b> -20W 3000lm, Type 3 ☆ <b>LCD</b> -24W 2400lm, Dark Sky ☆	<b>CCT</b> <b>C-4K</b>


**2017CL-50MH**



Acorns have 5 1/4" Neckless Opening  
See Page 80 for Replacements

☆ Lamp Included

**2018CL-50MH**



Posts accommodate Photo Control 320 or 688. See page 69. Posts sold separately.




**COMMERCIAL**







**C40T-**



Commercial LED standard in 4000K, Type V, other options available upon request. Integral surge suppression. 5 year warranty on LED components.


**GUIDE: C40TL-L40C-BK**



ITEM #	LENS	LIGHT SOURCE	COLOR
<b>C40T</b>	<b>ACRYLIC</b>	<b>LED LIGHT SOURCE</b>	
	<b>L-Opal Drop Lens</b> <b>FF-Frost Flat Lens</b>	<b>120-277v DEDICATED LED</b> <b>L40-40W 4000lm</b> <b>L60-60W 6000lm</b>	<b>CCT</b> <b>C-4K</b> <b>W-3K</b> <b>B-5K</b>
			<b>BK-Black</b> <b>BZ-Bronze</b> <b>WH-White</b>



SCAN FOR VIDEO



**C41T-**



**GUIDE: C41TC-L40C-BK**




ITEM #	LENS	LIGHT SOURCE	COLOR	OPTION
<b>C41T</b>	<b>GLASS</b> <b>C-Clear Lens</b>	<b>LED LIGHT SOURCE</b>		<b>T3-Type III Distribution</b>
		<b>120-277v DEDICATED LED</b> <b>L40-40W 3500lm</b> <b>L80-85W 6100lm</b>	<b>CCT</b> <b>C-4K</b> <b>WH-White</b>	
			<b>BK-Black</b> <b>BZ-Bronze</b> <b>WH-White</b>	

SPEC SHEETS AND IES FILES AVAILABLE ONLINE. Specifications subject to change without notice. LED option information on page 6.

**WAVE LIGHTING • PHONE 877.870.WAVE (9283)**

- LED & HID Models
- 0-10V Dimming LED Options
- LED Models Are DLC Listed

**C83TLA-**  
Style B Fitter




**C83T**

**C86T**

STYLE B FITTER

**C85TC-**  
Style A Fitter



**C84T**

**C85T**

STYLE A FITTER

Acorns have 8" Neck

See Page 81 for Acorn Replacements & Measurements



Commercial LED standard in 4000K, Type V, other options available upon request. Integral surge suppression. 5 year warranty on LED components.

**AFB**  
Plastic Finial Topper  
supplied with 1/4-20 x 1 1/4"  
Stainless Steel Hex Screw



## GUIDE: C84TC-L40C-BK-T3



ITEM #	ACORN	LIGHT SOURCE	COLOR	OPTIONS
<b>C83T</b> -Style B <b>C84T</b> -Style A <b>C85T</b> -Style A <b>C86T</b> -Style B	<b>POLYCARBONATE</b> C-Clear Textured <b>ACRYLIC</b> LA-Opal Textured CA-Clear Textured FA-Frost Textured	<b>LED LIGHT SOURCE</b> 120-277v DEDICATED LED L40-40W 4000lm L60-60W 6000lm E39 CORN COB LED 100-277v LC5-54W 7290lm, Type 5 ☆ LC3-40W 5600lm, Type 3 ☆ LCD-54W 5900lm, Dark Sky ☆	BK-Black BZ-Bronze WH-White	AFB-Acorn Finial Topper D- 0-10V Dimming (Dedicated LED Only) T3-Type III Distribution (Dedicated LED Only, T3 is Special Order, Type V Standard)

## GUIDE: C84TC-150MH-BK-HS



4Kv medium base socket standard in HID, Mogul Upon Request. 120V HPF integral ballast standard in HID models, specify voltage for multi-tap.

ITEM #	ACORN	LIGHT SOURCE	COLOR	OPTIONS
<b>C83T</b> -Style B <b>C84T</b> -Style A <b>C85T</b> -Style A <b>C86T</b> -Style B	<b>POLYCARBONATE</b> C-Clear Textured <b>ACRYLIC</b> LA-Opal Textured CA-Clear Textured FA-Frost Textured	<b>INCANDESCENT</b> (1) 200W MAX Medium Base <b>HPF MAGNETIC BALLAST</b> 100MH-(1) 100W Metal Halide ☆ 150MH-(1) 150W Metal Halide ☆ 100H-(1) 100W HPS ☆ 150H-(1) 150W HPS ☆	BK-Black BZ-Bronze WH-White	AFB-Acorn Finial Topper DSR-Dark Sky Reflector HS-House Shield MG-E39 Mogul Socket MT208-208v Multi-Tap MT240-240v Multi-Tap MT277-277v Multi-Tap R3-Type III Refractor R5-Type V Refractor (See Page 70 for Light Distribution)

★ Lamp Included  
Posts sold separately.

Not all options can be used in combination. Consult factory for details.

SPEC SHEETS AND IES FILES AVAILABLE ONLINE. Specifications subject to change without notice. LED option information on page 6.


**C91TC-**



**C94TC-**




- LED & HID Models
- 0-10V Dimming LED Options
- LED Models Are DLC Listed



**C91T**  
Small Hood

**C93T**  
Large Hood



**C92T**  
Small Hood

**C94T**  
Large Hood

STYLE A FITTER

STYLE B FITTER

**HS**  
House Shield



Acorns have 8" Neck  
See Page 81  
for Acorn  
Replacements &  
Measurements

**LED**  
COMMERCIAL  
system

Commercial LED standard in 4000K,  
Type V, other options available upon request.  
Integral surge suppression.  
5 year warranty on LED components.

**GUIDE: C91TC-L40C-BK-T3**



ITEM #	ACORN	LIGHT SOURCE	COLOR	OPTIONS
<b>C91T</b> -Style A	<b>POLYCARBONATE</b>	<b>LED LIGHT SOURCE</b>	<b>BK</b> -Black	<b>D</b> - 0-10V Dimming (Dedicated LED Only)
<b>C92T</b> -Style B	<b>C</b> -Clear Textured	<b>120-277v DEDICATED LED</b>	<b>BZ</b> -Bronze	<b>T3</b> -Type III Distribution (Dedicated LED Only, T3 is Special Order, Type V Standard)
<b>C93T</b> -Style A	<b>ACRYLIC</b>	<b>L40</b> -40W 4000lm	<b>WH</b> -White	
<b>C94T</b> -Style B	<b>LA</b> -Opal Textured	<b>L60</b> -60W 6000lm		
	<b>CA</b> -Clear Textured	<b>E39 CORN COB LED 100-277v</b>		
	<b>FA</b> -Frost Textured	<b>LC5</b> -54W 7290lm, Type 5 ☆		
		<b>LC3</b> -40W 5600lm, Type 3 ☆		
		<b>LCD</b> -54W 5900lm, Dark Sky ☆		
		<b>CCT</b>		
		<b>C-4K</b> (standard)		
		<b>W-3K</b> (special order)		
		<b>B-5K</b> (special order)		
		<b>C-4K</b> (standard)		



**GUIDE: C91TC-150MH-BK-HS**



ITEM #	ACORN	LIGHT SOURCE	COLOR	OPTIONS
<b>C91T</b> -Style A	<b>POLYCARBONATE</b>	<b>INCANDESCENT</b>	<b>BK</b> -Black	<b>DSR</b> -Dark Sky Reflector
<b>C92T</b> -Style B	<b>C</b> -Clear Textured	(1) 200W MAX Medium Base	<b>BZ</b> -Bronze	<b>HS</b> -House Shield
<b>C93T</b> -Style A	<b>ACRYLIC</b>	<b>HPF MAGNETIC BALLAST</b>	<b>WH</b> -White	<b>MG</b> -E39 Mogul Socket
<b>C94T</b> -Style B	<b>LA</b> -Opal Textured	<b>100MH</b> -(1) 100W Metal Halide ☆		<b>MT208</b> -208v Multi-Tap
	<b>CA</b> -Clear Textured	<b>150MH</b> -(1) 150W Metal Halide ☆		<b>MT240</b> -240v Multi-Tap
	<b>FA</b> -Frost Textured	<b>100H</b> -(1) 100W HPS ☆		<b>MT277</b> -277v Multi-Tap
		<b>150H</b> -(1) 150W HPS ☆		<b>R3</b> -Type III Refractor
				<b>R5</b> -Type V Refractor (See Page 70 for Light Distribution)

4Kv medium base socket standard in HID, Mogul Upon Request.

120V HPF integral ballast standard in HID models, specify voltage for multi-tap.

☆ Lamp Included


SPEC SHEETS AND IES FILES AVAILABLE ONLINE. Specifications subject to change without notice. LED option information on page 6.



### C75TC-


- LED & HID Models
- 0-10V Dimming LED Options
- LED Models Are DLC Listed

### C76TC-



**C75T**

STYLE A FITTER



**C76T**

STYLE B FITTER



Commercial LED standard in 4000K, Type V, other options available upon request. Integral surge suppression. 5 year warranty on LED components.

Acorns have 8" Neck  
See Page 81 for Acorn Replacements & Measurements

Other Acorn styles available. Contact Sales with questions.

### GUIDE: C75TC-L40C-BK-T3

ITEM #	ACORN	LIGHT SOURCE	COLOR	OPTIONS
<b>C75T</b> -Style A <b>C76T</b> -Style B	<b>POLYCARBONATE</b> C-Clear Textured <b>ACRYLIC</b> LA-Opal Textured CA-Clear Textured FA-Frost Textured	<b>LED LIGHT SOURCE</b> 120-277v DEDICATED LED L40-40W 4000lm L60-60W 6000lm E39 CORN COB LED 100-277v LC5-54W 7290lm, Type 5 ☆ LC3-40W 5600lm, Type 3 ☆ LCD-54W 5900lm, Dark Sky ☆	<b>CCT</b> C-4K(standard) W-3K(special order) B-5K(special order) <b>CCT</b> C-4K(standard)	<b>BK</b> -Black <b>BZ</b> -Bronze <b>WH</b> -White <b>D</b> - 0-10V Dimming (Dedicated LED Only) <b>T3</b> -Type III Distribution (Dedicated LED Only, T3 is Special Order, Type V Standard)



4Kv medium base socket standard in HID, Mogul Upon Request.

120V HPF integral ballast standard in HID models, specify voltage for multi-tap.

### GUIDE: C75TC-150MH-BK-HS

ITEM #	ACORN	LIGHT SOURCE	COLOR	OPTIONS
<b>C75T</b> -Style A <b>C76T</b> -Style B	<b>POLYCARBONATE</b> C-Clear Textured <b>ACRYLIC</b> LA-Opal Textured CA-Clear Textured FA-Frost Textured	<b>INCANDESCENT</b> (1) 200W MAX Medium Base <b>HPF MAGNETIC BALLAST</b> 100MH-(1) 100W Metal Halide ☆ 150MH-(1) 150W Metal Halide ☆ 100H-(1) 100W HPS ☆ 150H-(1) 150W HPS ☆	<b>BK</b> -Black <b>BZ</b> -Bronze <b>WH</b> -White	<b>DSR</b> -Dark Sky Reflector <b>HS</b> -House Shield <b>MG</b> -E39 Mogul Socket <b>MT208</b> -208v Multi-Tap <b>MT240</b> -240v Multi-Tap <b>MT277</b> -277v Multi-Tap <b>R3</b> -Type III Refractor <b>R5</b> -Type V Refractor (See Page 70 for Light Distribution)



Posts sold separately.



SPEC SHEETS AND IES FILES AVAILABLE ONLINE. Specifications subject to change without notice. LED option information on page 6.



**C77TC-**

- LED & HID Models
- 0-10V Dimming LED Options
- LED Models Are DLC Listed

**C78TC-**



Other Acorn styles available.  
Contact Sales with questions.

Acorns have 8" Neck  
See Page 81 for Acorn  
Replacements & Measurements



Commercial LED standard in 4000K,  
Type V, other options available upon request.  
Integral surge suppression.  
5 year warranty on LED components.

**GUIDE: C77TC-L40C-BK-T3**



ITEM #	ACORN	LIGHT SOURCE	COLOR	OPTIONS	
<b>C77T</b> -Style A <b>C78T</b> -Style B	<b>POLYCARBONATE</b>	<b>LED LIGHT SOURCE</b>		<b>BK</b> -Black <b>BZ</b> -Bronze <b>WH</b> -White	<b>AFB</b> -Acorn Finial Topper <b>D</b> - 0-10V Dimming (Dedicated LED Only) <b>T3</b> -Type III Distribution (Dedicated LED Only, T3 is Special Order, Type V Standard)
	<b>C</b> -Clear Textured <b>ACRYLIC</b> <b>CA</b> -Clear Textured	<b>120-277v DEDICATED LED</b> <b>L40</b> -40W 4000lm <b>L60</b> -60W 6000lm	<b>CCT</b> <b>C</b> -4K(standard) <b>W</b> -3K(special order) <b>B</b> -5K(special order)		
		<b>E39 CORN COB LED 100-277v</b> <b>LC5</b> -54W 7290lm, Type 5 ☆ <b>LC3</b> -40W 5600lm, Type 3 ☆ <b>LCD</b> -54W 5900lm, Dark Sky ☆	<b>CCT</b> <b>C</b> -4K(standard)		



**GUIDE: C78TC-150MH-BK-HS**



ITEM #	ACORN	LIGHT SOURCE	COLOR	OPTIONS
<b>C77T</b> -Style A <b>C78T</b> -Style B	<b>POLYCARBONATE</b>	<b>INCANDESCENT</b> (1) 200W MAX Medium Base	<b>BK</b> -Black <b>BZ</b> -Bronze <b>WH</b> -White	<b>AFB</b> -Acorn Finial Topper <b>DSR</b> -Dark Sky Reflector <b>HS</b> -House Shield <b>MG</b> -E39 Mogul Socket <b>MT208</b> -208v Multi-Tap <b>MT240</b> -240v Multi-Tap <b>MT277</b> -277v Multi-Tap <b>R3</b> -Type III Refractor <b>R5</b> -Type V Refractor (See Page 70 for Light Distribution)
	<b>C</b> -Clear Textured <b>ACRYLIC</b> <b>CA</b> -Clear Textured	<b>HPF MAGNETIC BALLAST</b> <b>100MH</b> -(1) 100W Metal Halide ☆ <b>150MH</b> -(1) 150W Metal Halide ☆ <b>100H</b> -(1) 100W HPS ☆ <b>150H</b> -(1) 150W HPS ☆		

4Kv medium base socket standard  
in HID, Mogul Upon Request.

120V HPF integral ballast standard in  
HID models, specify voltage for multi-tap.


☆ Lamp Included

SPEC SHEETS AND IES FILES AVAILABLE ONLINE. Specifications subject to change without notice. LED option information on page 6.

**WAVE LIGHTING • PHONE 877.870.WAVE (9283)**

- LED & HID Models
- 0-10V Dimming LED Options
- LED Models Are DLC Listed


**C2015TL-**



I.D. = 3"

*STYLE A FITTER*

**C2015T C8015T**  
Polycarbonate Globe Acrylic Globe



I.D. = 3"

*STYLE B FITTER*

**C2025T C8025T**  
Polycarbonate Globe Acrylic Globe

Globes have 8" Neck, See Page 81 for Replacements



Commercial LED standard in 4000K, Type V, other options available upon request. Integral surge suppression. 5 year warranty on LED components.

**24", 27", 30" & 36" Globes Available**  
**Contact Sales for Details**

### GUIDE: C2015TC-L40C-BK



ITEM #	ACORN	LIGHT SOURCE	COLOR	OPTIONS
<b>C2015T</b> -Style A <b>C2025T</b> -Style B	<b>POLYCARBONATE</b> C-Clear L-Opal S-Smoke P-Clear Prism	<b>LED LIGHT SOURCE</b> <b>120-277v DEDICATED LED</b> <b>L40</b> -40W 4000lm <b>L60</b> -60W 6000lm <b>E39 CORN COB LED 100-277v</b> <b>LC5</b> -54W 7290lm, Type 5 ☆ <b>LC3</b> -40W 5600lm, Type 3 ☆ <b>LCD</b> -54W 5900lm, Dark Sky ☆	<b>BK</b> -Black <b>BZ</b> -Bronze <b>WH</b> -White	<b>D</b> - 0-10V Dimming (Dedicated LED Only) <b>T3</b> -Type III Distribution (Dedicated LED Only, T3 is Special Order, Type V Standard)
<b>C8015T</b> -Style A <b>C8025T</b> -Style B	<b>ACRYLIC</b> C-Clear L-Opal S-Smoke P-Clear Prism			



### GUIDE: C2015TC-150MH-BK-HS



ITEM #	ACORN	LIGHT SOURCE	COLOR	OPTIONS
<b>C2015T</b> -Style A <b>C2025T</b> -Style B	<b>POLYCARBONATE</b> C-Clear L-Opal S-Smoke P-Clear Prism	<b>INCANDESCENT</b> (1) 200W MAX Medium Base <b>HPF MAGNETIC BALLAST</b> <b>100MH</b> -(1) 100W Metal Halide ☆ <b>150MH</b> -(1) 150W Metal Halide ☆ <b>100H</b> -(1) 100W HPS ☆ <b>150H</b> -(1) 150W HPS ☆	<b>BK</b> -Black <b>BZ</b> -Bronze <b>WH</b> -White	<b>DSR</b> -Dark Sky Reflector <b>HS</b> -House Shield <b>MG</b> -E39 Mogul Socket <b>MT208</b> -208v Multi-Tap <b>MT240</b> -240v Multi-Tap <b>MT277</b> -277v Multi-Tap <b>R3</b> -Type III Refractor <b>R5</b> -Type V Refractor (See Page 70 for Light Distribution)
<b>C8015T</b> -Style A <b>C8025T</b> -Style B	<b>ACRYLIC</b> C-Clear L-Opal S-Smoke P-Clear Prism			

☆ Lamp Included


4Kv medium base socket standard in HID, Mogul Upon Request.

120V HPF integral ballast standard in HID models, specify voltage for multi-tap.

SPEC SHEETS AND IES FILES AVAILABLE ONLINE. Specifications subject to change without notice. LED option information on page 6.


**FAX 330.630.1994 • WWW.WAVELIGHTING.COM**

**C2014TP-**



STYLE A FITTER

**C2014T** Polycarbonate Globe  
**C8014T** Acrylic Globe



STYLE B FITTER

**C2024T** Polycarbonate Globe  
**C8024T** Acrylic Globe

**C8024TC-**

(shown with R3)



Globes have 8" Neck. See Page 81 for Replacements



**GUIDE: C2014TL-L40C-BK-T3**



ITEM #	ACORN	LIGHT SOURCE	COLOR	OPTIONS
<b>C2014T-Style A</b> <b>C2024T-Style B</b>	<b>POLYCARBONATE</b> C-Clear L-Opal S-Smoke P-Clear Prism	<b>LED LIGHT SOURCE</b> <b>120-277v DEDICATED LED</b> L40-40W 4000lm L60-60W 6000lm <b>E39 CORN COB LED 100-277v</b> LC5-54W 7290lm, Type 5 ☆ LC3-40W 5600lm, Type 3 ☆ LCD-54W 5900lm, Dark Sky ☆	<b>BK-Black</b> <b>BZ-Bronze</b> <b>WH-White</b> CCT C-4K(standard) W-3K(special order) B-5K(special order)	<b>D- 0-10V Dimming</b> (Dedicated LED Only) <b>T3-Type III Distribution</b> (Dedicated LED Only, T3 is Special Order, Type V Standard)
<b>C8014T-Style A</b> <b>C8024T-Style B</b>	<b>ACRYLIC</b> C-Clear L-Opal S-Smoke P-Clear Prism		CCT C-4K(standard)	

Commercial LED standard in 4000K, Type V, other options available upon request. Integral surge suppression. 5 year warranty on LED components.

Posts sold separately.



4Kv medium base socket standard in HID, Mogul Upon Request.

120V HPF integral ballast standard in HID models, specify voltage for multi-tap.

☆ Lamp Included

**GUIDE: C2014TL-150MH-BK-HS**





ITEM #	ACORN	LIGHT SOURCE	COLOR	OPTIONS
<b>C2014T-Style A</b> <b>C2024T-Style B</b>	<b>POLYCARBONATE</b> C-Clear L-Opal S-Smoke P-Clear Prism	<b>INCANDESCENT</b> (1) 200W MAX Medium Base <b>HPF MAGNETIC BALLAST</b> 100MH-(1) 100W Metal Halide ☆ 150MH*-(1) 150W Metal Halide ☆ 100H-(1) 100W HPS ☆ 150H*-(1) 150W HPS ☆	<b>BK-Black</b> <b>BZ-Bronze</b> <b>WH-White</b>	<b>DSR-Dark Sky Reflector</b> <b>HS-House Shield</b> <b>MG-E39 Mogul Socket</b> <b>MT208-208v Multi-Tap</b> <b>MT240-240v Multi-Tap</b> <b>MT277-277v Multi-Tap</b> <b>R3-Type III Refractor</b> <b>R5-Type V Refractor</b> (See Page 70 for Light Distribution)
<b>C8014T-Style A</b> <b>C8024T-Style B</b>	<b>ACRYLIC</b> C-Clear L-Opal S-Smoke P-Clear Prism			

\*Not available with C8014T or C8024T

SPEC SHEETS AND IES FILES AVAILABLE ONLINE. Specifications subject to change without notice. LED option information on page 6.



- LED & HID Models
- 0-10V Dimming LED Options
- DLC LED Lamp Available



**LED**  
**COMMERCIAL**  
system

Commercial LED standard in 4000K, Type V, other options available upon request.  
Integral surge suppression.  
5 year warranty on LED components.

**C37TL-**



## GUIDE: C36TC-L40C-BK



ITEM #	LENS	LIGHT SOURCE	COLOR
<b>C36T</b> <b>C37T</b>	<b>ACRYLIC</b> L-Opal C-Clear	<b>LED LIGHT SOURCE</b>	<b>BK</b> -Black <b>BZ</b> -Bronze <b>WH</b> -White
		<b>120-277v DEDICATED LED</b> <b>L40</b> -40W 4000lm <b>L60</b> -60W 6000lm <hr/> <b>E39 CORN COB LED 100-277v</b> <b>LC5</b> -54W 7290lm, Type 5 ☆ <b>LC3</b> -40W 5600lm, Type 3 ☆ <b>LCD</b> -54W 5900lm, Dark Sky ☆	
		<b>CCT</b> <b>C</b> -4K <b>W</b> -3K <b>B</b> -5K <hr/> <b>CCT</b> <b>C</b> -4K(standard)	



4Kv medium base socket standard in HID, Mogul Upon Request.

120V HPF integral ballast standard in HID models, specify voltage for multi-tap.

★ **Lamp Included**

## GUIDE: C36TC-150MH-BK-R3



ITEM #	LENS	LIGHT SOURCE	COLOR	OPTIONS
<b>C36T</b> <b>C37T</b>	<b>ACRYLIC</b> L-Opal C-Clear	<b>INCANDESCENT</b> (1) 200W MAX Medium Base <b>HPF MAGNETIC BALLAST</b> <b>100MH</b> -(1) 100W Metal Halide ☆ <b>150MH</b> -(1) 150W Metal Halide ☆ <b>100H</b> -(1) 100W HPS ☆ <b>150H</b> -(1) 150W HPS ☆	<b>BK</b> -Black <b>BZ</b> -Bronze <b>WH</b> -White	<b>DSR</b> -Dark Sky Reflector <b>MG</b> -E39 Mogul Socket <b>MT208</b> -208v Multi-Tap <b>MT240</b> -240v Multi-Tap <b>MT277</b> -277v Multi-Tap <b>R3</b> -Type III Refractor <b>R5</b> -Type V Refractor (See Page 70 for Light Distribution)

SPEC SHEETS AND IES FILES AVAILABLE ONLINE. Specifications subject to change without notice. LED option information on page 6.



- LED & HID Models
- DLC LED Lamp Available



C59TF-



C32TP-



C33TP-

**LED**  
COMMERCIAL  
system

GUIDE: C32TC-L40C-BK-BP1

ITEM #	LENS	LIGHT SOURCE	COLOR	OPTIONS
C32T	ACRYLIC	<b>LED LIGHT SOURCE</b> 120-277v DEDICATED LED <b>L40-40W 4000lm</b> <b>L60-60W 6000lm</b>	<b>BK-Black</b> <b>BZ-Bronze</b> <b>WH-White</b>	<b>ACRYLIC BLACK OUT PANELS</b> <b>BP1-One Panel</b> <b>BP2-Two Panels</b> <b>BP3-Three Panels</b>
C33T	L-Opal P-Clear Prism			
C59T	GLASS F-Frosted	<b>E39 CORN COB LED 100-277v</b> <b>LC5-54W 7290lm, Type 5</b> ☆ <b>LC3-40W 5600lm, Type 3</b> ☆ <b>LCD-54W 5900lm, Dark Sky</b> ☆		



Commercial LED standard in 4000K, Type V, other options available upon request. Integral surge suppression. 5 year warranty on LED components.



4Kv medium base socket standard in HID, Mogul Upon Request.

120V HPF integral ballast standard in HID models, specify voltage for multi-tap.

☆ Lamp Included

GUIDE: C32TC-150MH-BK-R3


ITEM #	LENS	LIGHT SOURCE	COLOR	OPTIONS
C32T	ACRYLIC L-Opal P-Clear Prism	<b>INCANDESCENT</b> (1) 200W MAX Medium Base <b>HPF MAGNETIC BALLAST</b> <b>100MH-(1) 100W Metal Halide</b> ☆ <b>150MH-(1) 150W Metal Halide</b> ☆ <b>100H-(1) 100W HPS</b> ☆ <b>150H-(1) 150W HPS</b> ☆	<b>BK-Black</b> <b>BZ-Bronze</b> <b>WH-White</b>	<b>MG-E39 Mogul Socket</b> <b>MT208-208v Multi-Tap</b> <b>MT240-240v Multi-Tap</b> <b>MT277-277v Multi-Tap</b> <b>R3-Type III Refractor</b> <b>R5-Type V Refractor</b> (See Page 70 for Light Distribution)
C33T				
C59T	GLASS F-Frosted	<b>HPF MAGNETIC BALLAST</b> <b>100MH-(1) 100W Metal Halide</b> ☆ <b>70H-(1) 70W HPS</b> ☆ <b>100H-(1) 100W HPS</b> ☆ <b>150H-(1) 150W HPS</b> ☆		<b>ACRYLIC BLACK OUT PANELS</b> <b>BP1-One Panel</b> <b>BP2-Two Panels</b> <b>BP3-Three Panels</b>




SPEC SHEETS AND IES FILES AVAILABLE ONLINE. Specifications subject to change without notice. LED option information on page 6.

- LED & HID Models
- DLC LED Lamp Available

**C30TC-**



**C31TP-**



Commercial LED standard in 4000K, Type V, other options available upon request.  
Integral surge suppression.  
5 year warranty on LED components.

## GUIDE: C30TC-L40C-BK-T3

ITEM #	LENS	LIGHT SOURCE	COLOR	OPTIONS
C30T	GLASS COVER C-Clear	LED LIGHT SOURCE		<b>BK</b> -Black <b>BZ</b> -Bronze <b>WH</b> -White <b>T3</b> -Type III Distribution <small>(Dedicated LED Only, T3 is Special Order, Type V Standard)</small>
		<b>120-277v DEDICATED LED</b> <b>L40</b> -40W 4000lm <b>L60</b> -60W 6000lm	<b>CCT</b> <b>C</b> -4K	
C31T	ACRYLIC L-Opal P-Clear Prism	<b>120-277v DEDICATED LED</b> <b>L40</b> -40W 4000lm <b>L60</b> -60W 6000lm	<b>CCT</b> <b>C</b> -4K <b>W</b> -3K <b>B</b> -5K	<b>ACRYLIC BLACK OUT PANELS</b> <b>BP1</b> -One Panel <b>BP2</b> -Two Panels <b>BP3</b> -Three Panels
		<b>E39 CORN COB LED 100-277v</b> <b>LC5</b> -54W 7290lm, Type 5 ☆ <b>LC3</b> -40W 5600lm, Type 3 ☆ <b>LCD</b> -54W 5900lm, Dark Sky ☆	<b>CCT</b> <b>C</b> -4K(standard)	



4Kv medium base socket standard in HID, Mogul Upon Request.

120V HPF integral ballast standard in HID models, specify voltage for multi-tap.

★ Lamp Included

## GUIDE: C31TC-150MH-BK-HS

ITEM #	LENS	LIGHT SOURCE	COLOR	OPTIONS
C31T	ACRYLIC L-Opal P-Clear Prism	<b>INCANDESCENT</b> (1) 200W MAX Medium Base <b>HPF MAGNETIC BALLAST</b> <b>100MH</b> -(1) 100W Metal Halide ☆ <b>150MH</b> -(1) 150W Metal Halide ☆ <b>100H</b> -(1) 100W HPS ☆ <b>150H</b> -(1) 150W HPS ☆	<b>BK</b> -Black <b>BZ</b> -Bronze <b>WH</b> -White	<b>MG</b> -E39 Mogul Socket <b>MT208</b> -208v Multi-Tap <b>MT240</b> -240v Multi-Tap <b>MT277</b> -277v Multi-Tap <b>R3</b> -Type III Refractor <b>R5</b> -Type V Refractor <small>(See Page 70 for Light Distribution)</small> <b>ACRYLIC BLACK OUT PANELS</b> <b>BP1</b> -One Panel <b>BP2</b> -Two Panels <b>BP3</b> -Three Panels




SPEC SHEETS AND IES FILES AVAILABLE ONLINE. Specifications subject to change without notice. LED option information on page 6.

**FAX 330.630.1994 • WWW.WAVELIGHTING.COM**


- LED & HID Models
- DLC LED Lamp Available



**C35TF-**



**C34TF-**



**GUIDE: C34TC-L40C-BK**



ITEM #	LENS	LIGHT SOURCE	COLOR	OPTIONS
<b>C34T</b> <b>C35T</b>	<b>ACRYLIC</b> <b>F-Frosted</b>	<b>LED LIGHT SOURCE</b>	<b>BK-Black</b> <b>BZ-Bronze</b> <b>WH-White</b>	<b>ACRYLIC BLACK OUT PANELS</b> <b>BP1-One Panel</b> <b>BP2-Two Panels</b> <b>BP3-Three Panels</b>
		<b>120-277v DEDICATED LED</b> <b>L40-40W 4000lm</b>	<b>CCT</b> <b>C-4K</b> <b>W-3K</b> <b>B-5K</b>	
		<b>E39 CORN COB LED 100-277v</b> <b>LC5-54W 7290lm, Type 5</b> ☆ <b>LC3-40W 5600lm, Type 3</b> ☆ <b>LCD-54W 5900lm, Dark Sky</b> ☆	<b>CCT</b> <b>C-4K(standard)</b>	



4Kv medium base socket standard in HID, Mogul Upon Request.

120V HPF integral ballast standard in HID models, specify voltage for multi-tap.

☆ Lamp Included

**GUIDE: C34TC-150MH-BK-R3**




ITEM #	LENS	LIGHT SOURCE	COLOR	OPTIONS
<b>C34T</b> <b>C35T</b>	<b>ACRYLIC</b> <b>F-Frosted</b>	<b>INCANDESCENT</b> (1) 200W MAX Medium Base <b>HPF MAGNETIC BALLAST</b> <b>100MH-(1) 100W Metal Halide</b> ☆ <b>150MH-(1) 150W Metal Halide</b> ☆ <b>100H-(1) 100W HPS</b> ☆ <b>150H-(1) 150W HPS</b> ☆	<b>BK-Black</b> <b>BZ-Bronze</b> <b>WH-White</b>	<b>MG-E39 Mogul Socket</b> <b>MT208-208v Multi-Tap</b> <b>MT240-240v Multi-Tap</b> <b>MT277-277v Multi-Tap</b> <b>R3-Type III Refractor</b> <b>R5-Type V Refractor</b> (See Page 70 for Light Distribution) <b>ACRYLIC BLACK OUT PANELS</b> <b>BP1-One Panel</b> <b>BP2-Two Panels</b> <b>BP3-Three Panels</b>

SPEC SHEETS AND IES FILES AVAILABLE ONLINE. Specifications subject to change without notice. LED option information on page 6.

## 502VF

- DOWNLIGHT
- DIE CAST ALUMINUM



EXTENDS: 5 7/8"  
H/CTR: 2 1/4"  
BACKPLATE: 4 1/2" x 4 1/2"




See Page 23 for  
Non-Metallic Version

### GUIDE: 502VF-LR11W-BK

ITEM #	LENS	LIGHT SOURCE	COLOR
502V	GLASS F-Frosted	LED LIGHT SOURCE	
		120V LED LR11-11W, 870lm	CCT C-4K W-3K
			BK-Black BZ-Bronze

## 502SF

- UP & DOWNLIGHT
- DIE CAST ALUMINUM





EXTENDS: 5 7/8"  
H/CTR: 2 1/4"  
BACKPLATE: 4 1/2" x 4 1/2"



### GUIDE: 502SF-LR22W-BK

ITEM #	LENS	LIGHT SOURCE	COLOR
502S	GLASS F-Frosted	LED LIGHT SOURCE	
		120V LED LR22-22W, 1740lm	CCT C-4K W-3K
			BK-Black BZ-Bronze



Anchor Bolt M10 x 6.7"  
(3 anchor bolts and template included)

## C200BC



### GUIDE: C200BC-L10C-BK

ITEM #	LENS	LIGHT SOURCE	COLOR	OPTIONS
C200B	POLYCARB C-Clear	LED LIGHT SOURCE		D-0-10v Dimming
		100-277V MULTI-VOLT L10-10W, 937lm	CCT C-4K	
			BK-Black BZ-Bronze	


SPEC SHEETS AND IES FILES AVAILABLE ONLINE. Specifications subject to change without notice. LED option information on page 6.



- WALL OR CEILING MOUNT • INSECT & DUST PROOF
- ENCLOSED & GASKETED • DIE CAST ALUMINUM
- HOSE DOWN • IP65 RATED



**166FM**  
Ring



**169FM**  
Eyelid




SCAN FOR VIDEO



**GUIDE: 166FMF-LR15C-BK**

ITEM #	DIFFUSER	LIGHT SOURCE	COLOR	OPTION
<b>166FM</b>	<b>POLYCARBONATE</b>	<b>LED LIGHT SOURCE</b>	<b>BK-Black</b>	<b>O-Occupancy</b>
<b>169FM</b>	<b>F-Frosted</b>	<b>120V LIGHTWAVE LED</b>	<b>WH-White</b>	<b>Sensor</b>
		<b>LR15-15W 1400lm</b>	<b>C-4K</b>	
		<b>LR22-23W 1900lm</b>	<b>W-3K</b>	




- WALL MOUNT • INSECT & DUST PROOF
- ENCLOSED & GASKETED • PHOTOCELL INCLUDED
- HOSE DOWN • IP65 RATED



**GUIDE: 266FMF-LR12-BZ**

ITEM #	DIFFUSER/HOUSING	LIGHT SOURCE	COLOR
<b>266FM</b>	<b>POLYCARBONATE</b>	<b>LED LIGHT SOURCE</b>	<b>BZ-Bronze</b>
	<b>F-Frosted</b>	<b>120V LIGHTWAVE LED</b>	<b>CCT</b>
		<b>LR12-13W 1000lm</b>	<b>C-4K</b>




Energy Star Qualified Product

SPEC SHEETS AND IES FILES AVAILABLE ONLINE. Specifications subject to change without notice. LED option information on page 6.

**WAVE LIGHTING • PHONE 877.870.WAVE (9283)**

# ***POSTS & ACCESSORIES***





**S11T**  
See page 19

POST LENGTH	SUGG. BURIAL DEPTH
7'	18"
8'	18"
10'	24"
12'	24"
14'	30"

- Fits Most Standard 3" Post Top Fixtures
- Textured Powdercoated Aluminum
- Crossarm Included Unless Otherwise Specified
- Includes Inlet Hole
- Made In The USA




**GUIDE: 295-320NCA-BK**

**Dimensions:** O.D. = 2.950", I.D. = 2.850", Wall = .050"

ITEM #	OPTION	COLOR
295-7' Post	C-Conv. Outlet (338)	BK-Black
293-8' Post	320-Ezee Change Photo Control	WH-White
294-10' Post	NCA-No Crossarm	BZ-Bronze

**NOTE:** Crossarms available in black & white with gold balls, bronze posts ship with black crossarm. Posts with Crossarm, Photo Control, or Convenience Outlet come pre-punched for installation. Minor assembly required.



**BOLLARD & CUSTOM LENGTH POSTS (348) AVAILABLE ON Page 69**

**BK-BLACK**

**WH-WHITE**

**BZ-BRONZE**



7'  
8'  
10'

7'  
8'  
10'

**SAFETY NOTE:** Selecting posts and electrical accessories for performance and safety requires a full understanding of various factors and conditions. Professional engineering assistance in selecting these items is highly recommended. Purchaser is responsible for meeting any and all codes or requirements. If you choose a post or electrical accessory without getting such assistance, you do so at your own risk.

**2420**  
Decorative Base  
See page 68



Specifications subject to change without notice.




- Fits Most Standard 3" Post Top Fixtures
- 2 Piece Snap Together System, No Tools Required
- Constructed of Sturdy Cast Aluminum
- Available in Black Only

## GUIDE: C6P2-BK

ITEM #	COLOR
C6P2-6'	BK-Black
C8P2-8'	
C10P2-10'	



**C6P2-HW**  
Hardware Kit



Anchor Bolt 3/8" x 7"

6'


### C6P2-BK

**Post Dimensions:** O.D. = 3"  
I.D. = 2.8", Wall = .100", L = 6'

**Base Dimensions:**  
H = 21", W = 10 1/4"



**C8P2-HW**  
Hardware Kit



Anchor Bolt 3/8" x 12"

8'


### C8P2-BK

**Post Dimensions:** O.D. = 3"  
I.D. = 2.8", Wall = .100", L = 8'

**Base Dimensions:**  
H = 28 1/2", W = 11 5/8"  
2"x4" Hand Hole



**C10P2-HW**  
Hardware Kit



Anchor Bolt 3/8" x 12"

10'

### C10P2-BK

**Post Dimensions:** O.D. = 3"  
I.D. = 2.8", Wall = .100", L = 10'

**Base Dimensions:**  
H = 37", W = 16 5/8"  
2"x4" Hand Hole

**NOTE:** Includes anchor bolts and templates. Post and Base are two piece interlocking system that may ship separately.  
Post and Base Come as kit and cannot be sold separately.

**SAFETY NOTE:** Selecting posts for performance and safety requires a full understanding of various factors and conditions. Professional engineering assistance in selecting these items is highly recommended. Purchaser is responsible for meeting any and all codes or requirements. If you choose a post or electrical accessory without getting such assistance, you do so at your own risk.



Posts accommodate Photo Control 688. See page 69. Photo Controls sold separately.

Specifications subject to change without notice.

## DIRECT BURIAL ALUMINUM LAMP POSTS



- Fits Most Standard 3" Post Top Fixtures
- Textured Powdercoated Aluminum
- Includes Inlet Hole
- Made In The USA

### GUIDE: 2514-BK-320

**Post Dimensions:** O.D. = 2.950", Wall = .072"


ITEM #	COLOR	OPTION
2500-8'	<b>BK</b> -Black	<b>C</b> -Convenience Outlet
2510-10'	<b>WH</b> -White	<b>320</b> -Ezee Change Photo Control
2512-12'	<b>BZ</b> -Bronze	<b>688</b> -Button Photo Control
2514-14'		<b>HH*</b> -2"x4" Hand Hole

\*To meet U.L. and N.E.C. standards, any post designed to be mounted over 8' above ground includes a 2" x 4" (**HH**) Hand Hole and ground lug. **2512 & 2514** include Hand Hole unless otherwise specified.


**SEE PAGE 66 FOR .125" WALL DIRECT BURIAL OPTIONS**

### DIRECT BURIAL

**PUNCH LOCATIONS**  
for 8', 10', & 12' Posts  
(Side View)



**PUNCH LOCATIONS**  
for 14' Posts  
(Side View)



POST LENGTH	SUGG. BURIAL DEPTH
7'	18"
8'	18"
10'	24"
12'	24"
14'	30"

**SAFETY NOTE:** Selecting a post for performance and safety requires a full understanding of various factors and conditions. Professional engineering assistance in selecting a post is highly recommended.

Purchaser is responsible for meeting any and all codes or requirements. If you choose a post without getting such assistance, you do so at your own risk.



## SURFACE MOUNT ALUMINUM LAMP POSTS

- Fits Most Standard 3" Post Top Fixtures
- Textured Powdercoated Aluminum
- Made In The USA

### SURFACE MOUNT

Optional Flange Base & Cover

### GUIDE: 2600-STV-BZ

Post Dimensions: O.D. = 2.950", Wall = .072"

ITEM #	BASE TYPE	COLOR	OPTION
2600-8'	ST-Standard Base	BK-Black	C-Conv. Outlet
2610-10'	STV-ST Base w/Cover	BZ-Bronze	320-Ezee Change Photo Control
2612-12'	HD-Heavy Duty Base	WH-White	688-Button Photo Control
	HDV-HD Base w/Cover		HH*-2"x4" Hand Hole

\*To meet U.L. and N.E.C. standards, any post designed to be mounted over 8' above ground includes a 2" x 4" (HH) Hand Hole and ground lug. 2610 and 2612 include Hand Hole unless otherwise specified.

SEE PAGE 68 FOR COMPONENT OFFERINGS



(shown with STV option)



(shown with HDV option)

**PLEASE NOTE: YOU MUST SPECIFY BASE AND COVER WHEN ORDERING IN ORDER TO RECEIVE BASE AND COVER**

### GUIDE: 2690-HDV-BZ-HH

Post Dimensions: O.D. = 2.950", Wall = .125"



ITEM #	BASE TYPE	COLOR	OPTION
2690-10'	ST-Standard Base	BK-Black	C-Conv. Outlet
2692-12'	STV-ST Base w/Cover	BZ-Bronze	320-Ezee Change Photo Control
	HD-Heavy Duty Base	WH-White	688-Button Photo Control
	HDV-HD Base w/Cover		HH*-2"x4" Hand Hole

\*To meet U.L. and N.E.C. standards, any post designed to be mounted over 8' above ground includes a 2" x 4" (HH) Hand Hole and ground lug. 2690 and 2692 include Hand Hole unless otherwise specified.

SEE PAGE 68 FOR COMPONENT OFFERINGS

### SURFACE MOUNT


#### PUNCH LOCATIONS (Side View)



Anchor Bolt M8 x 12"



Die Cast Aluminum Flange base with anchor bolts for up to 12' x 2.950" O.D. Posts  
**ST-STANDARD BASE (2403)**



Anchor Bolt 3/8" x 12"



Heavy Duty Aluminum Flange base with anchor bolts for up to 14' x 2.950" O.D. Posts  
**HD-HEAVY DUTY BASE (2405)**




# Lamp Posts & Accessories

# 3" COMMERCIAL POSTS



Fits most 3" Post Top Fixtures  
Includes Inlet Hole



POST LENGTH	SUGG. BURIAL DEPTH
8'	18"
10'	24"
12'	24"
14'	30"

See Safety Note on page 67

## 3" ROUND ALUMINUM

.125 Wall Thickness

ITEM #	COLOR	OPTION
3588-8'	<b>BK</b> -Black	<b>C</b> -Conv. Outlet
3590-10'	<b>BZ</b> -Bronze	<b>320</b> -Ezee Change
3592-12'	<b>WH</b> -White	Photo Control
3594-14'		<b>688</b> -Button Photo Control
		<b>HH*</b>

## 3" FLUTED ALUMINUM

.125 Wall Thickness

ITEM #	COLOR	OPTION
3588F-8'	<b>BK</b> -Black	<b>688</b> -Button Photo Control
3590F-10'	<b>BZ</b> -Bronze	
3592F-12'	<b>WH</b> -White	<b>HH*</b>
3594F-14'		

## SURFACE MOUNTED

Powdercoated Aluminum. Welded Flange with Optional Decorative Cover. Anchor bolts included. Fits most 3" Post Top Fixtures. EPA ratings available on spec sheets.



**AB-AMERICANA** 2 PIECE COVER (3BC1)    **DB-DECOR** 2 PIECE COVER (3BC6)    **HX-HEXAGON** 2 PIECE COVER (3BC2)    **RB-ROUND** 1 PIECE COVER (3BC9)    **VB-VICTORIAN** 2 PIECE COVER (3BC3)

## 3" ROUND ALUMINUM


.125 Wall Thickness

ITEM #	BASE TYPE	COLOR	OPTION
3688-8'	<b>AB</b> -Americana	<b>BK</b> -Black	<b>C</b> -Conv. Outlet
3690-10'	<b>DB</b> -Decor	<b>BZ</b> -Bronze	<b>320</b> -Ezee Change
3692-12'	<b>HX</b> -Hexagon	<b>WH</b> -White	Photo Control
	<b>RB</b> -Round Cover		<b>688</b> -Button Photo Control
	<b>VB</b> -Victorian		<b>HH*</b>


## 3" FLUTED ALUMINUM

.125 Wall Thickness

ITEM #	BASE TYPE	COLOR	OPTION
3688F-8'	<b>AB</b> -Americana	<b>BK</b> -Black	<b>688</b> -Photo Control
3690F-10'	<b>DB</b> -Decor	<b>BZ</b> -Bronze	
3692F-12'	<b>HX</b> -Hexagon	<b>WH</b> -White	<b>HH*</b>
	<b>RB</b> -Round Cover		
	<b>VB</b> -Victorian		



3" Round    3" Fluted




Bolt Circle Pattern For 3" Posts  
Anchor Bolt 1/2" x 12"

\*To meet U.L. and N.E.C. standards, any post designed to be mounted over 8' above ground includes a 2" x 4" (**HH**) Hand Hole and ground lug. 3592, 3594, 3592F, 3594F, 3690, 3692, 3690F, and 3692F include Hand Hole unless otherwise specified.

SPEC SHEETS AND EPA RATINGS AVAILABLE ONLINE. Specifications subject to change without notice.

WAVE LIGHTING • PHONE 877.870.WAVE (9283)

Fits most 3" Post Top Fixtures  
Includes Inlet Hole



### SAFETY NOTES

All surface mount posts are supplied with welded mounting bases.

Selecting a post for performance and safety requires a full understanding of various factors and conditions. Professional engineering assistance in selecting a post is highly recommended. Purchaser is responsible for meeting any and all codes or requirements. If you choose a post without getting such assistance, you do so at your own risk.

**See Suggested Burial Depth on page 66**

### 4" ROUND ALUMINUM

.125 Wall Thickness

ITEM #	COLOR	OPTION
4590-10'	<b>BK-Black</b>	<b>HH*</b>
4592-12'	<b>BZ-Bronze</b>	
4594-14'	<b>WH-White</b>	

### 4" FLUTED ALUMINUM

.125 Wall Thickness

ITEM #	COLOR	OPTION
4590F-10'	<b>BK-Black</b>	<b>HH*</b>
4592F-12'	<b>BZ-Bronze</b>	
4594F-14'	<b>WH-White</b>	

## SURFACE MOUNTED

Powdercoated Aluminum. Welded Flange & 3" Tenon with Optional Decorative Cover. Anchor bolts included. Fits most 3" Post Top Fixtures. EPA ratings available on spec sheets.



**AB-AMERICANA**  
2 PIECE COVER  
(4BC1)



**DB-DECOR**  
2 PIECE COVER  
(4BC6)



**RB-ROUND**  
1 PIECE COVER  
(4BC9)



**VB-VICTORIAN**  
2 PIECE COVER  
(4BC3)

### 4" ROUND ALUMINUM


.125 Wall Thickness

ITEM #	BASE TYPE	COLOR	OPTION
4688-8'	<b>AB-Americanana</b>	<b>BK-Black</b>	<b>HH*</b>
4690-10'	<b>DB-Decor</b>	<b>BZ-Bronze</b>	
4692-12'	<b>RB-Round Cover</b>	<b>WH-White</b>	
4694-14'	<b>VB-Victorian</b>		



### 4" FLUTED ALUMINUM

.125 Wall Thickness

ITEM #	BASE TYPE	COLOR	OPTION
4688F-8'	<b>AB-Americanana</b>	<b>BK-Black</b>	<b>HH*</b>
4690F-10'	<b>DB-Decor</b>	<b>BZ-Bronze</b>	
4692F-12'	<b>RB-Round Cover</b>	<b>WH-White</b>	
4694F-14'	<b>VB-Victorian</b>		



Round F-Fluted  
4" Round 4" Fluted



Bolt Circle Pattern For 4" Posts  
Anchor Bolt 3/4" x 18"


\*To meet U.L. and N.E.C. standards, any post designed to be mounted over 8' above ground includes a 2" x 4" (**HH**) Hand Hole and ground lug. **4592, 4594, 4592F, 4594F, 4690, 4692, 4694, 4690F, 4692F, and 4694F** include Hand Hole unless otherwise specified.

Specifications subject to change without notice. SPEC SHEETS AND EPA RATINGS AVAILABLE ONLINE.

## CAST ALUMINUM & POLYCARBONATE POST TOP FITTERS


### Die Cast Aluminum

Medium Base Porcelain Socket, 4Kv Upon Request  
**Specify Option: (MG) Mogul Socket, (G) GU24 Socket**  
**Example: 1721-MG**



**1721** Black  
**1721B** Bronze  
**1720** White

For 10"-16" Globes and  
 11" x 17" Acorns with 5 1/4" Opening  
 Powdercoated Finish  
 I.D. = 3"




**1724** Black  
**1724B** Bronze  
**1724W** White

For 18" Globes with 5 1/4" Opening  
 Powdercoated Finish  
 I.D. = 3"

### Polycarbonate

Medium Base Phenolic Socket  
**Specify Option: (G) GU24 Socket**  
**Example: 1721P-G**



**1721P** Black  
**1720P** White


For 10"-16" Globes with 5 1/4" Opening  
 I.D. = 3"



### MOUNTING HARDWARE INCLUDED


Consult factory when ordering replacement fitters for fixtures with options: Refractors, Cylinders, etc.

## FLANGE BASES & COVERS



**2403**

Die Cast Aluminum Flange base, Powdercoated Finish  
 Anchor Bolts Included, for 8' -12' x 2.950" O.D. Posts only  
**SPECIFY: Black, (B) Bronze, or (W) White**



**2405**

Heavy Duty Aluminum Flange base, Powdercoated Finish  
 Anchor Bolts Included, for up to 14' x 2.950" O.D. Posts  
**SPECIFY: Black, (B) Bronze, or (W) White**

### Slip-On Polymer Decorative Post Cover



**2420**

Polyethylene Decorative Slip On  
 Base Cover for Standard 3" Post  
 I.D. = 3"

**SPECIFY: (B) Black (W) White**  
 No Hardware Included



Specifications subject to change without notice.



**2410**

Spun Aluminum Base  
 Cover for **2403**  
 Powdercoated Finish  
**SPECIFY: Black,  
 (B) Bronze, or (W) White**



**2411**

Spun Aluminum Base  
 Cover for **2405**  
 Powdercoated Finish  
**SPECIFY: Black,  
 (B) Bronze, or (W) White**



## POST FIXTURE ADAPTERS



.050" Wall Thickness




**348**

3" Custom Length Post for use with **347** Surface Mount Adapter

**SPECIFY:**

Color: **(BK)** Black, **(WH)** White or **(BZ)** Bronze

Length: **(XX)** must be in 6" intervals  
Example Part Number: **348-12**



**347**

Pier Mount Adapter for use with **348** Stub Post

**SPECIFY:**

**(BK)** Black  
**(WH)** White  
**(BZ)** Bronze



**349**

Pier Mount Adapter for 3" Post Mount Fixtures

**SPECIFY:**

**(BK)** Black  
**(WH)** White  
**(BZ)** Bronze



**CP-689**

**688** 120V Photo Control in hardware bag (assembly required) with Adaptor for 3" Posts

Not for use with commercial fixtures


**SPECIFY:**  
**(BK)** Black  
**(WH)** White

## POST ACCESSORIES



**335**

15" Aluminum Crossarm with Gold End Caps  
3/4" Dia. mounting hole required  
**SPECIFY:** Black or **(WH)** White



**HH**

2" x 4" Hand Hole Cover for 3" posts (includes mounting hardware)


**SPECIFY:** Black, **(B)** Bronze, or **(W)** White



**0500662** Black

**0500663** White

Crossarm Plugs for 3/4" Dia. hole



**HH4**

2" x 4" Hand Hole Cover for 4" posts (includes mounting hardware)

**SPECIFY:** Black, **(B)** Bronze, or **(W)** White

## PHOTOCONTROLS & OUTLETS FOR POST APPLICATIONS



**320**

120V for 3" Post with Ezee Change Plug, 1 3/8" Dia. mounting hole required  
Up to 300W Inc., 54W LED  
39W Fluor., 100W H.I.D.

**SPECIFY:** Black or **(W)** White


Specifications subject to change without notice.



**688**

120V Button Photo Control  
1 1/16" Dia. mounting hole required  
Up to 300W Inc., 54W LED  
39W Fluor., 100W H.I.D.

**SPECIFY:** Black



**338**

120V Grounded Convenience Outlet  
1 3/8" Dia. mounting hole required

**SPECIFY:** Black or **(W)** White

SEE SAFETY NOTE ON PAGE 62

## CAST ALUMINUM BRACKETS



**WB5**

Contemporary Wall Bracket pre-wired w/20" pigtail for easy installation with 3" Post Mount Fixture  
Max. Fixture Width: 16". I.D. = 3"  
H = 6", W = 4 1/2", E = 12 1/2"  
Powdercoated Finish  
**SPECIFY: (BK) Black (WH) White or (BZ) Bronze**



**PB5**

Post Bracket pre-wired w/20" pigtail for easy installation with 3" Post Mount Fixture.  
Designed to mount to Wave Lighting's 3" Commercial Posts. PB5-CAP Included.  
Max. Fixture Width: 16". I.D. = 3"  
H = 9 1/2", W = 4 1/2", E = 16 1/2"  
Powdercoated Finish  
**SPECIFY: (BK) Black (WH) White or (BZ) Bronze**

SEE  
PAGE 46



**PB5-2**

Post Bracket pre-wired w/20" pigtail for easy installation with 3" Post Mount Fixtures.  
Designed to mount 2 Fixtures to Wave Lighting's 3" Commercial Posts. PB5-CAP Incl.  
Max. Fixture Width: 16". I.D. = 3"  
H = 9 1/2", W = 4 1/2", E = 29"  
Powdercoated Finish  
**SPECIFY: (BK) Black (WH) White or (BZ) Bronze**



**PB5-3**

Post Bracket pre-wired w/20" pigtail for easy installation with 3" Post Mount Fixtures.  
Designed to mount 3 Fixtures to Wave Lighting's 3" Commercial Posts  
Max. Fixture Width: 14". I.D. = 3"  
H = 9", W = 4 1/2", E = 29"  
Powdercoated Finish  
**SPECIFY: (BK) Black (WH) White or (BZ) Bronze**



**PB5-CAP**

Cap for 3" Post I.D. = 3" Powdercoated Finish  
**SPECIFY: (BK) Black (WH) White or (BZ) Bronze**

See Safety Note on page 55

## CAST ALUMINUM FITTERS



**1784**

Style A Fitter for Globes & Acorns with 8" Neck  
H = 11", W = 10 1/4", I.D. = 3"



**1785**

Style B Fitter for Globes & Acorns with 8" Neck  
H = 10 1/2", W = 10 1/4", I.D. = 3"

4Kv Medium Base Porcelain Socket Standard


**Specify Option: (MG) Mogul Socket**  
Powdercoated Finish **Specify: (BK) Black, (BZ) Bronze or (WH) White**

## GLASS REFRACTORS




**1000135**

for Mogul Base Socket Type V Distribution  
H = 6 5/8", Dia. = 6 1/8"  
Top I.D. = 5 1/4"  
Bottom I.D. = 3 1/4"



**1000137**

for Mogul Base Socket Type III Distribution  
H = 6 5/8", Dia. = 6 1/8"  
Top I.D. = 5 1/4"  
Bottom I.D. = 3 1/4"



**1000138**

for Medium Base Socket Type V Distribution  
H = 4 7/8", Dia. = 4 3/4"  
Top I.D. = 4"  
Bottom I.D. = 3"

## DARK SKY REFLECTORS



**DS120**

Bottom Mount Kit for Mogul Base Sockets

**DS130**

Bottom Mount Kit for Medium Base Sockets



**DS140**

Bottom Mount Kit for 6" Glass Refractors (refractor not included)

## CAST ALUMINUM DECORATIVE BASE COVERS

Decorative Base Covers come as a two piece system, and can be installed over existing Surface Mounted Posts. **3BC9** and **4BC9** are one piece system.

### FOR MOST 3" DIAMETER POSTS



**3BC1**

Dia.: 13 1/8"  
Height: 24 1/8"



**3BC2**

Dia.: 11 1/2"  
Height: 13 5/8"



**3BC3**

Dia.: 11"  
Height: 26 3/8"



**3BC6**

Dia.: 11"  
Height: 9 5/8"



**3BC9**

Dia.: 10"  
Height: 3 1/2"  
Top I.D.: 4 1/8"

### FOR MOST 4" DIAMETER POSTS



**4BC1**

Dia.: 15"  
Height: 27 5/8"



**4BC3**

Dia.: 12 1/8"  
Height: 29"



**4BC6**

Dia.: 12"  
Height: 9 5/8"



**4BC9**


Dia.: 11"  
Height: 3 1/2"  
Top I.D.: 5 3/8"

Powdercoated Finish - **SPECIFY: (BK) Black, (BZ) Bronze or (WH) White**

Posts sold separately.

Specifications subject to change without notice.

# ***INDUSTRIAL***





# HIGH BAY

## LED HIGH BAY FIXTURES

- 120-277VAC
- 110W or 220W Available
- Estimated 50,000 hrs L<sub>70</sub>
- White or Glare Free Reflectors
- Optional Dome or Flat Lenses
- Suspended Mount Design
- Over 120 Lumens Per Watt
- Available in 5000k, 80 CRI
- 0-10V Dimming
- Spring Hook Included
- 5 Year Warranty
- DLC & UL Listed



SCAN FOR VIDEO




**C51H-**  
(reflective white reflector with optional frosted flat lens shown)


### GUIDE: C51HR-L100B-FF



ITEM #	REFLECTOR	LIGHT SOURCE	OPTIONS
<b>C51H</b>	<b>POLYCARBONATE</b> <b>R</b> -Reflective White (special order) <b>ACRYLIC</b> <b>F</b> -LED Frost	<b>LED LIGHT SOURCE</b> 100-277v DEDICATED LED <b>L100</b> -116W 14800lm	<b>CCT</b> <b>B</b> -5K
			<b>OPEN</b> No Lens Option <b>ENCLOSED</b> <b>CD</b> -Clear Dome Lens <b>FD</b> -Frosted Dome Lens <b>CF</b> -Clear Flat Lens <b>FF</b> -Frosted Flat Lens



### C51HR-L100B PHOTOMETRICS SHOWN




SPEC SHEETS AND IES FILES AVAILABLE ONLINE. Specifications subject to change without notice.

WAVE LIGHTING • PHONE 877.870.WAVE (9283)



# HIGH BAY



**Open**

Shown Without Lens Option



**Dome Lens**

**CD**-Clear Dome Lens  
**FD**-Frosted Dome Lens




**Flat Lens**

**CF**-Clear Flat Lens  
**FF**-Frosted Flat Lens



**C52H-**

(frost reflector with optional frosted dome lens shown)



## GUIDE: C52HF-L200B-FD



ITEM #	DIFFUSER	LIGHT SOURCE	OPTIONS
<b>C52H</b>	<b>POLYCARBONATE</b> <b>R</b> -Reflective White (special order)	<b>LED LIGHT SOURCE</b> 100-277v <b>DEDICATED LED</b> <b>L200</b> -209W 26800lm	<b>CCT</b> <b>B</b> -5K
	<b>ACRYLIC</b> <b>F</b> -LED Frost		
			<b>OPEN</b> No Lens Option  <b>ENCLOSED</b> <b>CD</b> -Clear Dome Lens <b>FD</b> -Frosted Dome Lens <b>CF</b> -Clear Flat Lens <b>FF</b> -Frosted Flat Lens

Specifications subject to change without notice. SPEC SHEETS AND IES FILES AVAILABLE ONLINE.

**FAX 330.630.1994 • WWW.WAVELIGHTING.COM**

## LED TEMPORARY WORK LIGHT


- 120-277VAC
- Estimated 50,000 hrs L<sub>70</sub>
- 60W or 100W Available
- 6' 18AWG Cord w/NEMA 5-15 Plug
- Omni-Directional Light
- OSHA Compliant
- Powdercoated Steel Lamp Guard
- Spring Hook Included
- Over 115 Lumens Per Watt
- Available in 5000k, 80 CRI
- UL Listed Dry & Damp
- 5 Year Warranty



GUIDE: C90H-LT60B

ITEM # LIGHT SOURCE

ITEM #	LIGHT SOURCE
C90H	<b>LED LIGHT SOURCE</b>
	100-277v DEDICATED LED
	LT60-60W 7000lm
	LT100-100W 13000lm
	CCT B-5K



Specifications subject to change without notice.

WAVE LIGHTING • PHONE 877.870.WAVE (9283)

# LED RETROFITS





## Easily Convert Existing Fixtures to LED with UL 1598C Classified Kits

- AC Driver-OnBoard
- 13W, 15W, & 23W Models
- Available in 3000K or 4000K
- Standard Mounting Options for Easy Install
- Optical Grade Polycarbonate Lens

- **Input Voltage:** 120VAC, 50/60hz
- **Constant Current Design**
- **High Power Factor >0.98**
- **Estimated 50,000 hrs L<sub>70</sub>**
- **Data Per NVLAP Laboratory**
- **On Board Line Surge & MOV Ground Surge Protection**

- **TRIAC Dimmable To 5%** (forward & reverse phase)
- **Mounting Hardware Available**
- **18" 18AWG Leads**
- **5 Year Limited Warranty**
- **FCC compliance Class B**
- **Energy Star CSD**



## GENERAL PURPOSE - For Open Residential Fixtures with Minimal Heat

**LRG6**




**Low Flicker  
Title 24 Available**  
(call for details)



**LRG8**




**SCAN FOR VIDEO**




### GUIDE: LRG6-LR12C

ITEM #	LIGHT SOURCE	CCT	OPTION
LRG6	120V LIGHTWAVE LED		H-Hardware
LRG8	LR12-13W 1000lm LR15-15W 1400lm LR22-23W 1900lm	C-4K W-3K	



**LRG10**



**Low Flicker  
Title 24 Available**  
(call for details)

### GUIDE: LRG10-LR32C

ITEM #	LIGHT SOURCE	CCT	OPTION
LRG10	120V LIGHTWAVE LED		H-Hardware
	LR12-13W 1000lm LR15-15W 1400lm LR22-23W 1900lm LR32-32W 2700lm	C-4K W-3K	



## HIGH HEAT - For Enclosed Residential Fixtures with Heat Concerns

### LRH3





### GUIDE: LRH3-LR12C

ITEM #	LIGHT SOURCE	OPTION
LRH3	120V LIGHTWAVE LED	CCT
	LR12-13W 1000lm	C-4K
LRH6	120V LIGHTWAVE LED	W-3K
	LR15-15W 1400lm	
	LR22-23W 1900lm	



### LRH6



Low Flicker Title 24 Available  
(call for details)



OPTIONAL HARDWARE PART # 10-268  
Optional Mounting Hardware Includes  
2ea. 8-32 X 3/8" Self Tapping Screws




OPTIONAL HARDWARE PART # 10-269  
Optional Mounting Hardware Includes  
2ea. #6 X 3/8" Self Tapping Screws

## COMMERCIAL RETROFIT KITS For Post Top Acorn Fixtures



### LRC



\*Height adjustable from 15" down to 10"

- Replaces Up To 250W Metal Halide
- For Enclosed Fixtures
- Telescoping Bracket
- Estimated 70,000 hrs L<sub>80</sub>
- Input Voltage: 100-277VAC, 50/60hz
- 0-10V Dimming Available
- Surge Protection
- 3000K\*, 4000K or 5000K\*, CRI 80
- Type 3 & Type 5 Models Available
- Universal Mounting Plate
- 20" 18AWG Leads
- 5 Year Limited Warranty
- UL 1598C Classified

### GUIDE: LRCL40C



ITEM #	LIGHT SOURCE	OPTION
LRC	120-277V LED	CCT
	L40-40W 4000lm	C-4K (Standard)
	L60-60W 6000lm	W-3K (Special Order)
		B-5K (Special Order)

D- 0-10V Dimming  
T3-Type III Distribution  
(T3 is Special Order, Type V is Standard)

SPEC SHEETS AND IES FILES AVAILABLE ONLINE. Specifications subject to change without notice. LED option information on page 6.

FAX 330.630.1994 • WWW.WAVELIGHTING.COM

## E26 MEDIUM BASE LAMPS For Residential Fixtures



**LCE26-9W**  
A19 LED Lamp  
9.5 Watt, 3000K, 800lm  
Replaces up to 60W Incandescent



**LCE26-9C**  
A19 LED Lamp  
9.5 Watt, 4000K, 800lm  
Replaces up to 60W Incandescent

- Replaces Up To 60W Incandescent
- For Enclosed Fixtures
- Dimmable
- E26 Medium Base for Easy Install
- Estimated 15,000 hrs L<sub>70</sub>
- Input Voltage: 120VAC, 50/60hz
- Surge Protection
- 3000K CCT 90CRI or 4000K CCT 80CRI
- 3 Year Limited Warranty
- UL Listed, Energy Star Certified & T24 Compliant (3K only)

## CORN COB LAMPS For Commercial & Light Commercial Fixtures

- Replaces Up To 250W Metal halide
- For Enclosed Fixtures
- E39 Mogul Base for Easy Install
- Estimated 50,000 hrs L<sub>70</sub>
- Input Voltage: 100-277VAC, 50/60hz
- Surge Protection
- 4000K, CRI 80
- Type 3, Type 5, & Dark Sky Models Available
- 5 Year Limited Warranty



**LCE39-24C-T5**  
Type 5 LED Lamp  
24Watt, 4000K, 3120lm  
Replaces up to 100W MH  
360° Beam Angle




**LCE39-20C-T3**  
Type 3 LED Lamp  
20Watt, 4000K, 3000lm  
Replaces up to 100W MH  
180° Adjustable Beam Angle




**LCE39-24C-DS**  
Dark Sky LED Lamp  
24Watt, 4000K, 2400lm  
Replaces up to 100W MH  
180° Down Beam Angle



**LCE39-54C-T5**  
Type 5 LED Lamp  
54Watt, 4000K, 7290lm  
Replaces up to 250W MH  
360° Beam Angle



**LCE39-40C-T3**  
Type 3 LED Lamp  
40Watt, 4000K, 5600lm  
Replaces up to 250W MH  
180° Adjustable Beam Angle



**LCE39-54C-DS**  
Dark Sky LED Lamp  
54Watt, 4000K, 5900lm  
Replaces up to 250W MH  
180° Down Beam Angle



SPEC SHEETS AND IES FILES AVAILABLE ONLINE. Specifications subject to change without notice. LED option information on page 6.

**WAVE LIGHTING • PHONE 877.870.WAVE (9283)**



# ***DIFFUSERS***



## LENSES & DIFFUSERS

### ENDURACAST GLASS

#### 544XF-LENS

Frosted  
use with 544VF,  
544HCF, & 544TF

#### 544SF-LENS

Frosted  
use with 544SF

#### 549VF-LENS

Frosted  
use with 549VF

#### 549SF-LENS

Frosted  
use with 549SF

#### 561FMF-LENS


Frosted  
use with 561FMF

#### C200BC-LENS

Frosted  
use with C200BC


#### 502XF-LENS

Frosted  
use with 502SF & 502VF




### COLONIAL, SAXONY & VANGUARD WALL MOUNT ACRYLIC

\*144-Clear Bvl Dia    145-Amber Bvl Dia  
146-Clear Bvl    147-Frosted Bvl



### COMPANION SIZE EVERSTONE™ LANTERNS ACRYLIC

1301724-Clear    1301725-Opal  
\*1301726-Frosted




### WALL PACK EVERSTONE™ LANTERNS ACRYLIC

\*1301727-Clear Prismatic  
1301728-Opal



### VICTORIAN LANTERN ACRYLIC

\*1300371-Opal  
1300372-Black



### COLONIAL, SAXONY & VANGUARD POST TOP ACRYLIC

148-Clear Bvl    149-Frosted Bvl  
\*153-Amber Bvl Dia    154-Clear Bvl Dia



### FULL SIZE EVERSTONE™ LANTERNS ACRYLIC

1301733-Clear    1301734-Frosted  
\*1301735-Opal



### LANTERN CHIMNEY GLASS

\*1300316-Frosted



### VICTORIAN LANTERN ACRYLIC

\*1300373-Clear Lens  
w/Trim Ring (sold assembled)

\*Item Shown

## GLOBES & ACORNS W/5 1/4" NECKLESS OPENING



### CLEAR POLYCARBONATE

1256-12"  
1456-14"  
1656-16"  
1856-18"

### ACRYLIC

1066-10"  
1266-12"  
1466-14"  
1666-16"  
1866-18"



### OPAL POLYCARBONATE

1255-12"  
1455-14"  
1655-16"  
1855-18"

### ACRYLIC

1065-10"  
1265-12"  
1465-14"  
1665-16"  
1865-18"



### SMOKE POLYCARBONATE

1258-12"  
1458-14"  
1658-16"  
1858-18"

### ACRYLIC

1068-10"  
1268-12"  
1468-14"  
1668-16"  
1868-18"



### CLEAR PRISMATIC POLYCARBONATE

1859-18"

### ACRYLIC

1069-10"  
1269-12"  
1669-16"  
1869-18"



### CLEAR TEXTURED POLYCARBONATE

1756-For 2017CL  
1766-For 8017CL

### OPAL TEXTURED POLYETHYLENE

1776-For 9017



### CLEAR TEXTURED POLYCARBONATE

2067-For 2018CL  
2057-For 8018CL

### OPAL TEXTURED POLYETHYLENE

2077-For 9018

## GLOBES & ACORNS W/4" FITTER NECK



ACRYLIC  
0800407-8" Clear  
0800408-8" Opal



ACRYLIC  
0800411-12" Clear  
0800410-12" Opal



POLYCARBONATE  
1467-Clear  
ACRYLIC  
0801410-Opal








## SUGGESTED MAX WATTAGES

SIZE	ACRYLIC			POLYCARBONATE			POLYETHYLENE		
	INC.	FLUOR.	H.I.D.	INC.	FLUOR.	H.I.D.	INC.	FLUOR.	H.I.D.
10"	75W	18W	--	--	18W	--	--	--	--
12"	100W	26W	--	100W	26W	--	--	--	--
14"	150W	32W	--	150W	32W	--	--	--	--
16"	150W	32W	70W	150W	32W	70W	--	--	--
18"	150W	32W	100W	150W	32W	100W	--	--	--
ACORNS	INC.	FLUOR.	H.I.D.	INC.	FLUOR.	H.I.D.	INC.	FLUOR.	H.I.D.
1756	--	--	--	150W	32W	70W	--	--	--
2067	--	--	--	150W	32W	70W	--	--	--

Suggested Max Wattages is for use as a general reference chart only. No warranty or guarantee is expressed or implied, as product suitability is determined by installation.




Specifications subject to change without notice.

## ACRYLIC LENSES



## 8" FITTER NECK OPENING GLOBES

24", 27", 30" & 36" Globes Available  
Contact Sales with Questions



### SUGGESTED MAX WATTAGES

SIZE	ACRYLIC		POLYCARBONATE	
	INC.	H.I.D.	INC.	H.I.D.
18"	150W	100W	150W	250W
20"	150W	150W	150W	250W
ACORNS	INC.	H.I.D.	INC.	H.I.D.
0801390	--	--	150W	250W
0801391	--	--	150W	250W
0801392	--	--	150W	250W
3467	--	--	150W	250W

Suggested Max Wattages is for use as a general reference chart only. No warranty or guarantee is expressed or implied, as product suitability is determined by installation.

## 8" FITTER NECK OPENING ACORNS



\* For Finial - **SPECIFY: (DR)** Drill Hole \*\* For Hood - **SPECIFY: (TR)** Trim Top For C91 and C92, **(TR2)** Trim Top For C93 and C94

Specifications subject to change without notice.



# NUMERICAL INDEX

<u>ITEM #</u>	<u>PAGE</u>	<u>ITEM #</u>	<u>PAGE</u>	<u>ITEM #</u>	<u>PAGE</u>	<u>ITEM #</u>	<u>PAGE</u>
AFB	49	C8014T	54	S761WF	26	165FM	34
CP-689	69	C8015T	53	S77WF	27	166FM	16, 60
C6P2	63	C8024T	54	S771WF	27	167FM	24
C8P2	63	C8025T	53	S772WF	26	168FM	10
C10P2	63	DS120	70	S79WF	27	169FM	16, 60
C30T	57	DS130	70	S791WF	26	170FM	11
C31T	57	DS140	70	WB5	70	172FM	11
C31T(P/L)-LENS	81	HH	69	3BC1	70	173FM	12
C32T	56	HH4	69	3BC2	70	174FM	12
C32T(P/L)-LENS	81	HS	50	3BC3	70	178FM	10
C33T	56	LCE26	78	3BC6	70	204S	29
C33T(P/L)-LENS	81	LCE39	78	3BC9	70	204T	29
C34T	58	LRC	77	4BC1	70	204V	29
C34TF-LENS	81	LRG6	76	4BC3	70	206VC	28
C35T	58	LRG8	76	4BC6	70	208S	28
C36T	55	LRG10	76	4BC9	70	208T	28
C36T(C/L)-LENS	81	LRH3	77	15RP2	34	209	36
C37T	55	LRH6	77	105	37	210	36
C37T(C/L)-LENS	81	PB5-CAP	70	106	37	211	36
C40T	48	PB5	70	109	37, 42, 44	212	36
C41T	48	PB5-2	70	110	37, 42, 44	215	36
C51H	72	PB5-3	70	111	37	216	36
C52H	73	S11S	19	112	37	217	36
C90H	74	S11T	19	113	38	220S	30
C59T	56	S11V	19	114	38	220T	30
C59TF-LENS	81	S21S	18	115	38, 42, 44	230S	32
C75T	51	S21T	18	116	38, 42, 44	230T	32
C76T	51	S21V	18	123	38	240S	31
C77T	52	S26S	20	124	38	240T	31
C78T	52	S26T	20	144	80	240V	31
C83T	49	S26V	20	145	80	241VC	31
C84T	49	S27SC	21	146	80	260S	32
C85T	49	S27TC	21	147	80	260T	32
C86T	49	S32W	21	148	80	263FM	35
C91T	50	S33W	22	149	80	264FM	35
C92T	50	S34W	23	153	80	265FM	35
C93T	50	S35W	23	154	80	270S	30
C94T	50	S75TC	25	156FM	33	270T	30
C200B	17, 59	S75TC-1/2	25	157FM	33	293	62
C200BC-LENS	80	S75TL-1/2	25	160FM	11	294	62
C2014T	54	S75VC	24	161FM	11	295	62
C2015T	53	S75VL	24	162FM	11	320	69
C2024T	54	S759V	24	163FM	11	335	69
C2025T	53	S76WF	27	164FM	34	338	69

# NUMERICAL INDEX

<u>ITEM #</u>	<u>PAGE</u>	<u>ITEM #</u>	<u>PAGE</u>	<u>ITEM #</u>	<u>PAGE</u>	<u>ITEM #</u>	<u>PAGE</u>
347	69	1269	80	2002	41	3692F	66
348	69	1455	80	2003	41, 46	4590	67
349	69	1456	80	2004	41, 46	4590F	67
407	39	1458	80	2017CL	41, 46	4592	67
408	39	1465	80	2018CL	41, 46	4592F	67
409	39, 43, 45	1466	80	2055-8N	81	4594	67
410	39, 43, 45	1468	80	2056-8N	81	4594F	67
411	39	1655	80	2058-8N	81	4688	67
412	39	1656	80	2059-8N	81	4688F	67
420	36	1658	80	2065-8N	81	4690	67
421	36	1665	80	2066-8N	81	4690F	67
422	36	1666	80	2057	80	4692	67
502SF	17	1668	80	2067	80	4692F	67
502VF	17	1669	80	2068-8N	81	4694	67
502XF-LENS	80	1720	68	2069-8N	81	4694F	67
544HC	15	1720P	68	2077	80	8000	41
544S	15	1721	68	2403	68	8001	41
544XF-LENS	80	1721B	68	2405	68	8002	41
544T	15	1721P	68	2410	68	8003	41, 46
544V	15	1724	68	2411	68	8004	41, 46
549S	14	1724B	68	2420	68	8017CL	41, 46
549SF-LENS	80	1724W	68	2500	64	8018CL	41, 46
549V	14	1756	80	2510	64	9017	41
549VF-LENS	80	1766	80	2512	64	9018	41
561FM	14	1776	80	2514	64	801390	81
561FMF-LENS	80	1784	70	2600	65	801391	81
607	40	1785	70	2610	65	801392	81
608	40	1855	80	2612	65	500662	69
609	40, 43, 45	1855-8N	81	2690	65	500663	69
610	40, 43, 45	1856	80	2692	65	1000135	70
611	40	1856-8N	81	3467	81	1000137	70
612	40	1858	80	3588	66	1000138	70
688	69	1858-8N	81	3588F	66	1300316	80
785	29	1859	80	3590	66	1300371	80
1065	80	1859-8N	81	3590F	66	1300372	80
1066	80	1865	80	3592	66	1300373	80
1068	80	1865-8N	81	3592F	66	1301724	80
1069	80	1866	80	3594	66	1301725	80
1255	80	1866-8N	81	3594F	66	1301726	80
1256	80	1868	80	3688	66	1301727	80
1258	80	1868-8N	81	3688F	66	1301728	80
1265	80	1869	80	3690	66	1301733	80
1266	80	1869-8N	81	3690F	66	1301734	80
1268	80	2001	41	3692	66	1301735	80



phone: 330.630.9187 • fax: 330.630.1994

**877.870.WAVE (9283)**

[www.wavelighting.com](http://www.wavelighting.com)

The logo for Wave Lighting is centered in the lower half of the page. It features the word "WAVE" in a large, bold, blue, italicized sans-serif font. Below it, the word "LIGHTING" is written in a smaller, blue, italicized sans-serif font. The text is set against a background of vibrant, multi-colored waves (blue, purple, green, yellow, orange, red) that are rendered as a series of fine, overlapping lines, creating a sense of motion and depth. The waves are set against a dark, almost black background.

**WAVE**  
**LIGHTING**