

SPORTS LIGHTING



THE #1 PICK IN SPORTS LIGHTING SPECIFICATION

- Structurally stronger than competitor lamps
- Better performance
- Electrically neutral frame



VENTURE
LIGHTING

LIGHTING SOLUTIONS



Job: Various Sporting Facilities

Venture Product: 1500 watt Sport 60 Lamps

Lights that Bring Their A-Game

From a little league team to the professional games in Major League Baseball, great lighting is an essential part of any sporting event. It is vital to the audience experience and the player's game because it ensures that each participant can easily view the events on the field and keep track of the score. Venture Lighting's Metal Halide 1500 and 1650W lighting systems are the technology of choice for focusing light in sporting events and producing a brilliant white light that stands up to the most extreme heat or chilling cold. This impressive system assists in the effective display of team colors and stadium features through its unparalleled, color rendering light quality.

An example of this impressive lighting system can be seen while visiting the home of the Boston Red Sox Farm Team at Lelacher Park in Lowell, Massachusetts. This 5,000 seat stadium features 115 of Venture Lighting's 1500W Horizontal Sport Lamps and hosts many of Lowell University's spring and fall baseball games. Unaffected by changes in temperature, this lighting technology enables fans to enjoy their favorite sports teams and athletes in the best possible light.

Benefits:

- Position oriented, horizontal applications up to 60° tilt
- Unique cross pinch design for stable light output
- High lumen output (1650 watt), 177,000 lumens and 107 lumens per watt for optimal horizontal and vertical illuminance
- 3200K - 4000K color



HIGH WATTAGE SPORTS LIGHTING

1000 WATT Open Rated LAMPS ANSI Type-O ANSI M47/O

Lamp Description	Product No.	Initial Lumens	LLD	LPW	Rated Life (hrs)	CCT	CRI	Finish	Oper. Pos.	Fig.	Case Qty	Additional Notes
MPI 1000W/BU	62948	107000	0.65	107	12000	3500K	65	Clear	BU±15°	M1	6	

Enclosed Rated PROBE START LAMPS ANSI Type-E Mogul Base

Watts	Lamp Description	Product No.	ANSI Code	Initial Lumens	LLD	LPW	Rated Life (hrs)	CCT	CRI	Finish	Oper. Pos.	Fig.	Case Qty	Additional Notes
1000	MS 1000W/V/LU/BT37	35892	S52/E	110000	0.65	110	15000	4000K	65	Clear	V±15°	G1	6	
1000	MH 1000W/U	72051	M47/E	110000	0.65	110	12000	4000K	65	Clear	U	I1	6	
1000	MH 1000W/U/BT37	15332	M47/E	110000	0.65	110	12000	4000K	65	Clear	U	G1	6	
1000	MH 1000W/U/5K	35914	M47/E	80000	0.65	80	9000	5000K	75	Clear	U	I1	6	
1000	MS 1000W/BU	89113	M47/E	115000	0.65	115	12000	4000K	65	Clear	BU±15°	I1	6	
1000	MS 1000W/BU/BT37	13090	M47/E	115000	0.65	115	12000	4000K	65	Clear	BU±15°	G1	6	
1000	MS 1000W/HOR/BT37/3K	53702	M47/E	115000	0.75	115	12000	3400K	70	Clear	HOR±45°	Q1	6	
1000	MS 1000W/HOR/BT37/4K	80091	M47/E	110000	0.65	110	12000	4000K	70	Clear	HOR±45°	Q1	6	
1000	MS 1000W/HOR/SPORT 60	47503	M47/E	115000	0.75	115	12000	3400K	70	Clear	HOR±60°	J1	6	
1000	MS 1000W/BU/T25	78952	M47/E	110000	0.60	110	5000	4000K	65	Clear	BU±15°	K1	6	
1500	MH 1500W/HBU	18360	M48/E	161000	0.85	107	3000	3400K	65	Clear	BU±105°	I1	6	
1500	MH 1500W/U/XL	12342	M48/E	170000	0.80	113	6000	4000K	65	Clear	U	I1	6	
1500	MS 1500W/HOR/XP/SPORT 60	82070	M48/E	162000	0.85	108	3000	3400K	70	Clear	HOR±60°	P1	6	
1650	MS 1650W/HOR/XP/SPORT 60	16419	M112/E	177000	0.82	107	3000	3200K	70	Clear	HOR±60°	P1	6	



Benefits


- Brighter - high lumen output
- "Extra Life" lamp available - Venture's MH 1500W/U/XL lamp has a 6,000 hour rated life
- Venture's Sport 60 lamps are designed for sports lighting angles
- Compact BT37 for excellent optical control (MS 1000/HOR/BT37)
- High lumen output for efficient design
- Good color rendition (65-70 CRI)



Dia. = 4.6" (120mm)
MOL = 11.5" (292mm)
LCL = 7.0" (178mm)
Base = Mogul (E39)



Dia. = 7.0" (180mm)
MOL = 15.3" (391mm)
LCL = 9.5" (241mm)
Base = Mogul (E39)




Dia. = 7.0" (180mm)
MOL = 15.3" (391mm)
LCL = 9.5" (241mm)
Base = Mogul POMB (EP39)




Dia. = 3.1" (79mm)
MOL = 11.5" (292mm)
LCL = 7.0" (178mm)
Base = Mogul (E39)



Dia. = 7.0" (180mm)
MOL = 15.4" (391mm)
LCL = 9.5" (241mm)
Base = Mogul (EX39)



Dia. = 7.0" (180mm)
MOL = 15.3" (391mm)
LCL = 9.5" (241mm)
Base = Mogul POMB (EP39)



Dia. = 4.6" (120mm)
MOL = 11.5" (292mm)
LCL = 7.0" (178mm)
Base = Mogul POMB (EP39)



LIGHTING UPGRADE SOLUTIONS

UPGRADE SYSTEM UNITS

Save Time & Money

Use an existing fixture reflector and get all the benefits of an energy-saving lighting upgrade system

- Cost is less than a new fixture
- Save up to 465 watts per luminaire and achieve up to 120 lamp lumens per watt
- Saves labor costs and avoids unnecessary warranty issues

See our brochure online



SUPER PULSE START Long Life (SPL)

Extended Life Lamp Series

Venture's Super Pulse Start Long Life lamp series delivers up to twice the rated life of many of our regular pulse start products

- 40,000 hours rated life
- Patent pending for long life
- Quartz metal halide
- 70W to 875W, Available in Universal, Vertical ($\pm 15^\circ$), Base-Up ($\pm 15^\circ$) and Horizontal ($\pm 75^\circ$) positions of operation

See our brochure online



SUPER PULSE START Ceramic (SPC)

Ceramic Metal Halide

Venture's Super Pulse Start Ceramic lamps achieve warm, crisp, white light, high CRI and reveal vibrant colors.

- Superior Color Performance
- Best in Class Performance for Lumen Output, Color and Life
- Warm, Crisp 3000K CCT or 4200K and Up to 90 CRI

See our brochure online



PRECISION GLASS OPTICS

VENTURE'S JEWEL™ REFLECTOR

- Prismatic glass reflector
- Increase existing light levels while reducing energy consumption when using Venture's Uni-Form pulse-start lamp and ballast systems

See our brochure online



LEAFNUT™

WIRELESS LIGHTING CONTROL SYSTEM

Achieve energy savings and reduces carbon emissions through Venture's advanced intelligent wireless control system for area or street lighting. LeafNut™ system is a complete 24/7 web-based, easy-to-install, wireless communications control system.

See our brochure online



RIO SYSTEMS

RETROFIT INTEGRATED OPTICS

Brilliant ceramic metal halide with optimized electronic power supply and highly efficient (95%) reflective glass optic - Like a whole new fixture, without the cost!

- More Light and Less Energy
- Simple Solution, Delivers Quality White Light
- Fully Adjustable Cut-Off

See our brochure online



(800) 451-2606
or (440) 248-3510

Fax: (800) 451-2605
7905 Cochran Road
Glenwillow, Ohio 44139 USA
E-mail: venture@adlt.com

VentureLighting.com



VENTURE
LIGHTING