



A history of innovation.  
**A solution for every  
challenge.**





## Legrand/Pass & Seymour keeps the innovations coming.

At Legrand/Pass & Seymour, we've been providing real solutions to real problems for so long, it's almost second nature. From the world's first GFCI receptacle in 1971, to the introduction of ground-breaking SafeLock™ Protection some 30 years later, we've been delivering GFCI innovations designed to enhance safety, shorten installation times, and increase productivity for nearly four decades.

Because of their proven effectiveness, GFCIs are required by code in numerous locations. We've made it our mission to offer intelligently designed solutions for every residential and commercial environment.

Whether the jobs call for receptacles, combination devices, portable, tamper-resistant, weather-resistant, RoHS-compliant, government stimulus-compliant, hospital grade, or specification grade — there's a reliable P&S GFCI innovation for you.

Read on and learn more about our full line of GFCI products.



**High-impact-resistant, thermoplastic construction** for superior strength and durability.

**Illumination life** expectancy exceeds 20 years, eliminating the need to change bulbs.

**The most durable GFCI available.** Exceeds UL943 voltage surge requirements; survives 100x the required UL 3kA/6kV voltage surge test cycles.

**LED nightlight** turns ON at dusk and OFF at dawn automatically.

**Trip indicator light** makes it easy to identify a tripped condition.

**Two back-wire holes** per termination add wiring flexibility, eliminate pigtail, and save box space.

**Automatic shutter system** prevents young children from inserting common household objects, but releases to accommodate plugs.


1595NTLTRWCC4

**Ground terminal back-wire clamp** for fast installation.

**Patented SafeLock™ Protection** — if critical components are damaged and ground fault protection is lost, power to receptacle is disconnected.

**Prevents line-load reversal miswire:** no power to the face or downstream receptacles if wired incorrectly.

**FSUL Listed** (Federal Specification WC596)



# A safety solution for every home.

## IT ALL COMES DOWN TO KEEPING PEOPLE SAFE.

That was our goal when we invented the first GFCI receptacle, and it remains our singular focus to this day. Our broad product line includes all the residential GFCI devices you'd expect from an industry leader, plus a number of truly innovative solutions designed to meet today's (and tomorrow's) special requirements.



1595TRW

### **Tamper-Resistant GFCI — helps keep children safe.**

- Patented shutter system helps prevent insertion of foreign objects
- Patented SafeLock™ Protection — if critical components are damaged and ground fault protection is lost, power to receptacle is disconnected
- Meets *NEC*® requirements



1595SWTTRWCC4

### **Decorator Switch/GFCI Combination Devices — ideal for remodeling.**

- User-preferred up-and-down switching combined with standard GFCI safety features
- Provides more function in single-gang opening
- Tamper-Resistant for added safety
- Ideal for bath and kitchen vent fans



1595TRNAW



### **RoHS-compliant GFCI — designed to meet environmental regulations.**

- Meet all the requirements of the Restriction of Hazardous Substances regulations
- Provides the same functionality and protection as our traditional GFCI





1595NTLTRWCC4

## Make nighttime navigation automatic.


Ideal for bathrooms, hallways, kitchens, stairs, nurseries, and more, this award-winning device delivers advanced safety and protection.

### **Tamper-Resistant Nightlight/GFCI combination — ensures safety and convenience.**

- Sealed nightlight with Lexan® lens prevents tampering
- LED illumination with a 20+ year life expectancy means no bulbs to change
- Photocell turns nightlight ON in the dark — OFF in the daylight



### OTHER SUGGESTED PRODUCTS



### **Single-Gang Flush Mount While-In-Use Covers**

- Meet *NEC*® requirements for outdoor power
- Corner hinges enable horizontal or vertical installation

### **Weatherproof While-In-Use Covers**

- Corner hinges enable horizontal or vertical installation
- Easy-opening one-finger latch



**SPEED AND RELIABILITY ARE THE KEY** to successful commercial installations. Our GFCIs are designed to meet those needs... and then some. That's because we've been offering GFCIs longer than anyone else, so we know what you need to do the job right the first time. Take a look at our innovative line — we'll think you'll find a solution that perfectly matches your needs. Every time.



PT2095NTLTR, PT2095W



2095W

2095WL



## P&S PlugTail™ GFCI — the fastest-installing GFCI ever. Period.

- Beats tough deadlines on any commercial job
- Patented plug and connector design enables simultaneous, one-click termination of all terminals
- No exposed terminals creates a finger-safe application before, during, and after installation
- Available in Spec Grade, Hospital Grade, Tamper-Resistant, and LED/Nightlight combinations

### Specification Grade GFCI

- 20 amp designed for heavy commercial use
- One-quarter-inch thinner than competing GFCIs, giving the installer more room in the box
- The most durable GFCI available. Exceeds UL943 voltage surge requirements; survives 100x the required UL 3kA/6kV voltage surge test cycles

### Illuminated GFCI — quickly identifies use of back-up power.

- Green LED indicator light ON when power is available

# Innovations that translate into faster commercial installations.



2095DSWRBK

## Weather-Resistant DuraShield™ GFCI — designed extra rugged for long service life.

- Designed for harsh outdoor environments
- Listed to the Weather-Resistant supplement of UL 498
- Rubber curtains let plug blades in, keep dust, water, and insects out
- Integral sealing gasket protects critical electronic components; oversized gasket seals wall box opening



2095HGNTLRW

## Hospital Grade GFCI

- Meets rigorous requirements of Hospital Grade supplement of UL 498
- Available in Tamper-Resistant, Illuminated with green indicator ON light, and LED/Nightlight combinations



2095TRNALA, PT2095HGNALA

## Stimulus-Compliant GFCIs — designed to meet new government regulations.

- GFCIs that meet the requirements of the Buy American provision of the American Recovery and Reinvestment Act
- Provides the same functionality and protection as our traditional GFCI


## Residential GFCI Receptacles



Catalog Number	Description	Color	Ratings		NEMA Config. No.
			A.	V.	
<b>TradeMaster®/Spec Grade Tamper-Resistant 15 Amp Duplex GFCI</b>					
1595TR*	Decorator	I, W, —, BK, LA, BN, TI	15	125	5-15R
1595TRS*	with Auto-Ground	I, W, LA			
<b>TradeMaster®/Spec Grade 15 Amp Duplex GFCI</b>					
1595*	Decorator	I, W, —, GRY, BK, RED, LA	15	125	5-15R
1595S*	with Auto-Ground	I, W, LA			
<b>Combination Tamper-Resistant Single-Pole Switch/GFCI</b>					
1595SWTR*CC4	Switch Rating: 15A, 120VAC	I, W, BK, LA	15	125	5-15R
<b>Combination Tamper-Resistant 15 Amp Nightlight/GFCI</b>					
1595NTLTR*CC4	Decorator	I, W, BK, LA, BN, TI	15	125	5-15R
<b>TradeMaster®/Spec Grade Weather-Resistant 15 Amp Duplex GFCI</b>					
1595TRWR*	Decorator	I, W, —, LA	15	125	5-15R
<b>RoHS-Compliant TradeMaster®/Spec Grade Tamper-Resistant 15 Amp Duplex GFCI</b>					
1595TRR*	Decorator	I, W, LA	15	125	5-15R

### Third-Party Compliance:

cULus Listed, File Number E140596, Standard UL498, Federal Specification WC596



## Commercial GFCI Receptacles

### \*Color Designation

I	Ivory
W	White
GRY	Gray
BK	Black
RED	Red
LA	Light Almond
BN	Brushed Nickel
TI	Titanium
—	Brown

Catalog Number	Description	Color	Ratings		NEMA Config. No.
			A.	V.	
<b>Spec Grade Tamper-Resistant 20 Amp Duplex GFCI</b>					
2095TR*	Decorator	I, W, —, GRY, BK, RED, LA	20	125	5-20R
2095TRS*	with Auto-Ground	I, W, LA			
<b>Spec Grade 20 Amp Duplex GFCI</b>					
2095*	Decorator	I, W, —, GRY, BK, RED, LA	20	125	5-20R
2095S*	with Auto-Ground	I, W, LA			
<b>Hospital Grade Tamper-Resistant Duplex GFCI</b>					
1595HGTR*	15 Amp	I, W, —, GRY, RED, LA	15	125	5-15R
2095HGTR*	20 Amp		20	125	5-20R
<b>Hospital Grade Duplex GFCI</b>					
1595HG*	15 Amp	I, W, —, GRY, RED, LA	15	125	5-15R
2095HG*	20 Amp		20	125	5-20R
<b>Hospital Grade Illuminated 20 Amp Duplex GFCI</b>					
2095HG*L	Decorator	I, W, RED	20	125	5-20R
<b>Specification Grade Illuminated 20 Amp Duplex GFCI</b>					
2095*L	Decorator	I, W, LA	20	125	5-20R
<b>Combination Tamper-Resistant 20 Amp Nightlight/GFCI</b>					
2095NTLTR*	Decorator	I, W, GRY, LA	20	125	5-20R
<b>Hospital Grade Combination Tamper-Resistant Nightlight/GFCI</b>					
1595HGNTLTR*	15 Amp	I, W, —, GRY, RED, LA	15	125	5-15R
2095HGNTLTR*	20 Amp		20	125	5-20R
<b>Specification Grade Weather-Resistant 20 Amp Duplex GFCI</b>					
2095TRWR*	Decorator	I, W, —, GRY, LA	20	125	5-20R
<b>Specification Grade Weather-Resistant DuraShield™ Duplex GFCI</b>					
1595DSWRBKCC4	15 Amp	BK	15	125	5-15R
2095DSWRBK	20 Amp		20	125	5-20R
<b>RoHS-Compliant TradeMaster®/Spec Grade Tamper-Resistant 20 Amp Duplex GFCI</b>					
2095TRR*	Decorator	I, W, LA	20	125	5-20R



## P&S PlugTail™ GFCI Receptacles

Catalog Number	Description	Color	Ratings		NEMA Config. No.
			A.	V.	
<b>Spec Grade Duplex GFCI</b>					
PT1595*	15 Amp	I, W, —, GRY, BK, RED, LA	15	125	5-15R
PT2095*	20 Amp		20	125	5-20R
<b>Spec Grade Tamper-Resistant Duplex GFCI</b>					
PT1595TR*	15 Amp	I, W, —, GRY, BK, RED, LA	15	125	5-15R
PT2095TR*	20 Amp		20	125	5-20R
<b>Hospital Grade Duplex GFCI</b>					
PT1595HG*	15 Amp	I, W, —, GRY, RED, LA	15	125	5-15R
PT2095HG*	20 Amp		20	125	5-20R
<b>Hospital Grade Tamper-Resistant Duplex GFCI</b>					
PT1595HGTR*	15 Amp	I, W, GRY, RED, LA	15	125	5-15R
PT2095HGTR*	20 Amp		20	125	5-20R
<b>Spec Grade Tamper-Resistant Combination Nightlight/GFCI</b>					
PT1595NTLTRI	15 Amp	Ivory	15	125	5-15R
PT2095NTLTR*	20 Amp	I, W	20	125	5-20R
<b>Hospital Grade Tamper-Resistant Combination Nightlight/GFCI</b>					
PT1595HGNTLTR*	15 Amp	I, W, RED	15	125	5-15R
PT2095HGNTLTR*	20 Amp	I, W, LA	20	125	5-20R



## NAFTA-Compliant GFCI Receptacles



Catalog Number	Description	Color	Ratings		NEMA Config. No.
			A.	V.	
<b>NAFTA-Compliant TradeMaster®/Spec Grade Tamper-Resistant Duplex GFCI</b>					
1595TRNA*	15 Amp	I, W, —, GRY, BK, LA	15	125	5-15R
2095TRNA*	20 Amp		20	125	5-20R
<b>NAFTA-Compliant TradeMaster®/Spec Grade Duplex GFCI</b>					
1595NA*	15 Amp	I, W, —, GRY, BK, LA	15	125	5-15R
2095NA*	20 Amp		20	125	5-20R
<b>NAFTA-Compliant Hospital Grade Tamper-Resistant 20 Amp Duplex GFCI</b>					
2095HGTRNA*	Decorator	I, W, GRY, RED, LA	20	125	5-20R
<b>NAFTA-Compliant Hospital Grade Duplex GFCI</b>					
1595HGNA*	15 Amp	I, W, RED	15	125	5-15R
2095HGNA*	20 Amp	I, W, —, GRY, RED, LA	20	125	5-20R

*Color Designation
I Ivory
W White
GRY Gray
BK Black
RED Red
LA Light Almond
BN Brushed Nickel
TI Titanium
— Brown

## NAFTA-Compliant P&S PlugTail™ GFCI Receptacles

Catalog Number	Description	Color	Ratings		NEMA Config. No.
			A.	V.	
<b>NAFTA-Compliant Spec Grade Duplex GFCI</b>					
PT1595NA*	15 Amp	I, W, GRY, LA	15	125	5-15R
PT2095NA*	20 Amp	I, W, —, GRY, BK, LA	20	125	5-20R
<b>NAFTA-Compliant Spec Grade Tamper-Resistant 20 Amp Duplex GFCI</b>					
PT2095TRNA*	Decorator	I, W, GRY, LA	20	125	5-20R
<b>NAFTA-Compliant Spec Grade Tamper-Resistant Combination Nightlight/GFCI</b>					
PT1595NTLTRNA*	15 Amp	I, W	15	125	5-15R
PT2095NTLTRNA*	20 Amp		20	125	5-20R

**designed to be better.™**

For additional technical or application-specific information, call 800-223-4185 or visit our website at [www.legrand.us/PassandSeymour](http://www.legrand.us/PassandSeymour). We're eager to put our expertise to work for you.

**Distributed by:**



**Pass & Seymour**

P.O. Box 4822  
Syracuse, NY 13221-4822  
800-776-4035  
[www.legrand.us/PassandSeymour](http://www.legrand.us/PassandSeymour)

**Legrand Canada**  
570 Applewood Crescent  
Vaughan, ON, L4K 4B4  
Phone: 905.738.9195, Fax: 905.738.9721  
[www.legrand.ca](http://www.legrand.ca)