

Eaton's
AL series dimmers

One dimmer. Many solutions.

Featuring the latest in dimming technology

Lighting control you can count on

EATON

Powering Business Worldwide

Right dimmer. Every time.



Eaton's AL series dimmers offer flexibility in design with the latest dimming technology

Flexibility & innovation

Eaton's Wiring Devices' AL series dimmers offer a versatile option for any dimming application - fine tune the dimming performance to match your exact needs and change colors as needed to suit any décor.

Color flexibility

Color change kits come with three color faceplates, offering design flexibility within one product. Select models are available in 4 different color combination packs.



- Single-pole or 3-way wiring in one unit
- Separate ON/OFF and DIM/BRIGHT controls allow easy return to favorite light levels
- Interchangeable faceplates available in 4 different color change kit options



A	W	V
---	---	---

C1 Color Kit
Almond, White, Ivory

LA	W	V
----	---	---


C2 Color Kit
Light Almond, White, Ivory

BK	W	V
----	---	---

C4 Color Kit
Black, White, Ivory

BK	W	GY
----	---	----

C5 Color Kit
Black, White, Gray



Count on flexibility -
one dimmer handles common lighting loads.

Count on lower inventory cost -
includes an interchangeable color kit.

Count on saving time and money -
the right dimmer every time!






Lighting control you can count on

AL series dimmers provide rating flexibility

Enjoy flexibility and optimal dimming performance with a variety of light sources and functionality

Dimmer features	Smart AL dimmer (AAL06)	Decorator AL dimmer (DAL06P)	Slide AL dimmer (SAL06P)	Toggle AL dimmer (TAL06P1)
Rapid start feature	Selectable ON or OFF	Fully adjustable	Fixed ON	Fully adjustable
Adjustable high-end trim	✓	–	–	–
Adjustable low-end trim	✓	✓	✓	✓
Wiring configurations	Single-pole or multi-location	Single-pole or 3-way	Single-pole or 3-way	Single-pole or 3-way
Color change kits	✓	✓	–	✓

Rated for common lighting loads

	Dimmable Light-Emitting Diodes (LED)
	Dimmable Compact Fluorescent (CFL)
	Electronic & Magnetic Low-Voltage (ELV & MLV)
	Incandescent/Halogen (INC/HAL)
	Fluorescent (FLR)



AAL06



DAL06P



SAL06P



TAL06P1

AL series dimmers



Single-pole and multi-location

- Green LEDs indicate light level and preset
- Separate DIM/BRIGHT bar can be used to adjust preset level when lights are ON or OFF
- Air gap switch allows for manual disconnect during lamp changes

Color change faceplate options



AAL06
(PJS26W wallplate
sold separately)

Smart AL series dimmers

Features

- Electro-mechanical push pad for ON/OFF operation with separate DIM/BRIGHT bar
- 10-second delayed OFF feature
- Selectable Rapid Start feature to ensure lamp start-up at low preset light levels
- LED light level display for presetting illumination levels and master/accessory units for multi-location control
- Adjustable high-end and low-end trimming
- No de-rating required for CFL/LED in multi-gang installations
- Each color kit package includes 3 colors

Smart dimmers, wire leads

Rating W	V/AC	Compatible lamp types	Description	Color suffix	Catalog no.
300	120	Dimmable LED/CFL	Smart dimmer master, AL series, Single-pole/multi-location with presets and LEDs. Neutral required.	C1, C2, C4, C5	□ AAL06-___
600	120	INC, HAL, FLR, MLV, ELV			
___	120	___	Accessory dimmer, multi-location with presets and LEDs. Must be used with AAL06	A, B, BK, GY, LA, V, W, C1, C2	□ ARD-___
___	___	___	Master dimmer color change faceplate	A, B, BK, GY, LA, V, W	□ AMC-___-BP
___	___	___	Accessory dimmer color change faceplate	A, B, BK, GY, LA, V, W	□ ARC-___-BP

See instruction sheet for de-rating information

Color ordering information

For ordering devices, include Cat. no. followed by the color code: A (Almond), B (Brown), BK (Black), GY (Gray), LA (Light Almond), V (Ivory), W (White), C1 (Color Change Kit - Almond, White, Ivory), C2 (Color Change Kit - Light Almond, White, Ivory), C4 (Color Change Kit - Black, White, Ivory), C5 (Color Change Kit - Black, White, Gray)

A	B	BK	GY	LA	V	W					
(Almond)	(Brown)	(Black)	(Gray)	(Lt. Almond)	(Ivory)	(White)					
A	W	V	LA	W	V	BK	W	V	BK	W	GY
C1 Color Kit Almond, White, Ivory			C2 Color Kit Light Almond, White, Ivory			C4 Color Kit Black, White, Ivory			C5 Color Kit Black, White, Gray		

Testing & code compliance cULus Listed to UL1472 file no. E47967 NOM Certified. Material characteristics environmental: Flammability meets UL 94 requirements; V2 rated Temperature rating: 0°C to 40°C (32°F to 104°F)
Specifications and availability subject to change without notice.



AL series dimmers



Single-pole and 3-way

- Separate DIM/BRIGHT bars allows lights to be returned to favorite settings
- Adjustable low-end trim setting improves lamp compatibility
- Fully adjustable Rapid Start ensures the right amount of power boost during start-up

Color change faceplate options



Decorator AL series dimmers

Features

- Preset feature allows user to return to previous light level when turning lights ON
- Adjustable low-end dimming range
- Fully adjustable Rapid Start setting for optimal lamp start-up at low preset light levels
- No de-rating required in multi-gang installations
- Each color kit package includes 3 colors



DAL06P
(PJS26W wallplate
sold separately)

Decorator dimmers, back & side wire

Rating W	Compatible V/AC	Compatible lamp types	Description	Color suffix	Catalog no.
300	120	Dimmable LED/CFL	Decorator dimmer, Single-pole/3-way preset	C1, C2, C4, C5	<input type="checkbox"/> DAL06P-__
600	120	INC, HAL, FLR, MLV, ELV			
—	—	—	DAL06P Color change faceplate	A, BK, GY, LA, V, W	<input type="checkbox"/> DCK1-__

See instruction sheet for de-rating information

Color ordering information

For ordering devices, include Cat. no. followed by the color code: A (Almond), B (Brown), BK (Black), GY (Gray), LA (Light Almond), V (Ivory), W (White), C1 (Color Change Kit - Almond, White, Ivory), C2 (Color Change Kit - Light Almond, White, Ivory), C4 (Color Change Kit - Black, White, Ivory), C5 (Color Change Kit - Black, White, Gray)

A	BK	GY	LA	V	W						
(Almond)	(Black)	(Gray)	(Lt. Almond)	(Ivory)	(White)						
A	W	V	LA	W	V	BK	W	V	BK	W	GY
C1 Color Kit			C2 Color Kit			C4 Color Kit			C5 Color Kit		
Almond, White, Ivory			Light Almond, White, Ivory			Black, White, Ivory			Black, White, Gray		

Testing & code compliance cULus Listed to UL1472 file no. E47967 NOM Certified. Material characteristics environmental: Flammability meets UL 94 requirements; V2 rated Temperature rating: 0°C to 40°C (32°F to 104°F)
Specifications and availability subject to change without notice.



AL series dimmers



Single-pole and 3-way

- Adjustable low-end dim setting improves lamp compatibility
- Separate DIM/BRIGHT slider allows lights to be returned to favorite setting
- Green LED locator light glows softly when lights are OFF
- Large ON/OFF switch makes turning lights ON and OFF easy

Slide AL series dimmers

Features

- Preset feature allows user to return to previous light level when turning lights ON
- Adjustable low-end dimming range
- Fixed Rapid Start provides quick power burst to ensure lights start even at low preset light levels
- No de-rating required in multi-gang installations



SAL06P-W
(PJS26W wallplate
sold separately)

Slide dimmers, back & side wire

Rating W	Rating V/AC	Compatible lamp Types	Description	Color suffix	Catalog no.
300	120	Dimmable LED/CFL	Slide dimmer, Single-pole/3-way preset	A, BK, GY, LA, V, W	□ SAL06P-__
600	120	INC, HAL, FLR, MLV, ELV			

See instruction sheet for de-rating information

Color ordering information

For ordering devices, include Cat. no. followed by the color code: A (Almond), BK (Black), GY (Gray), LA (Light Almond), V (Ivory), W (White)


A	BK	GY	LA	V	W
(Almond)	(Black)	(Gray)	(Lt. Almond)	(Ivory)	(White)

Testing & code compliance cULus Listed to UL1472 file no. E47967 NOM Certified. Material characteristics environmental: Flammability meets UL 94 requirements; V2 rated Temperature rating: 0°C to 40°C (32°F to 104°F)

Specifications and availability subject to change without notice.



AL series dimmers



Single-pole and 3-way

- Green LED locator light glows softly when lights are OFF
- Adjustable low-end dim setting improves lamp compatibility
- Separate DIM/BRIGHT bars allows lights to be returned to favorite settings
- Fully adjustable Rapid Start ensures the right amount of power boost during start-up

Color change faceplate options



Toggle AL series dimmers

Features

- Preset feature allows user to return to previous light level when turning lights ON
- Adjustable low-end dimming range
- Fully adjustable Rapid Start setting for optimal lamp start-up at low preset light levels
- No de-rating required in multi-gang installations
- Each color kit package includes 3 colors



TAL06P1
(PJS1W wallplate
sold separately)


Toggle dimmers, back & side wire

Rating W	Compatible V/AC	Compatible lamp types	Description	Color suffix	Catalog no.
300	120	Dimmable LED/CFL	Toggle dimmer, Single-pole/3-way preset	C1, C2, C4, C5	□ TAL06P1-__
600	120	INC, HAL, FLR, MLV, ELV			□ TAL06P1-__
—	—	—	TAL06P Color change faceplate	A, BK, GY, LA, V, W	□ TCK2-__

See instruction sheet for de-rating information

Color ordering information

For ordering devices, include Cat. no. followed by the color code: A (Almond), B (Brown), BK (Black), GY (Gray), LA (Light Almond), V (Ivory), W (White), C1 (Color Change Kit - Almond, White, Ivory), C2 (Color Change Kit - Light Almond, White, Ivory), C4 (Color Change Kit - Black, White, Ivory), C5 (Color Change Kit - Black, White, Gray)



Testing & code compliance cULus Listed to UL1472 file no. E47967 NOM Certified. Material characteristics environmental: Flammability meets UL 94 requirements; V2 rated Temperature rating: 0°C to 40°C (32°F to 104°F)

Specifications and availability subject to change without notice.



Visit our website:
www.Cooperwiringdevices.com/ALseries

Electrical Sector
203 Cooper Circle
Peachtree City, GA 30269
United States
Eaton.com
Cooperwiringdevices.com

Electrical Sector
Canada Operations
5925 McLaughlin Road
Mississauga, Ontario, L5R 1B8
Canada
EatonCanada.ca
Cooperwiringdevices.com

Electrical Sector
Mexico Operations
Carr. Tlalnepantla -
Cuautitlán Km 17.8 s/n
Col. Villa Jardín esq.
Cerrada 8 de Mayo
Cuautitlán, México CP 54800
México
Eaton.mx
Cooperwiringdevices.com

Eaton
1000 Eaton Boulevard
Cleveland, OH 44122
United States
Eaton.com

© 2015 Eaton
All Rights Reserved
Printed in USA
Publication No. BR610009EN
July 2015

Eaton is a registered trademark.

All other trademarks are property
of their respective owners.