

the radiant[®] collection
CATALOG



the radiant[®] collection



Legrand, North America

60 Woodlawn Street
West Hartford, CT 06110
1.877.BY.LEGRAND (295.3472)
www.legrand.us/radiant

570 Applewood Crescent
Vaughan, Ontario L4K 4B4
905.738.9195
www.legrand.ca/radiant

©2017 Legrand. All Rights Reserved. PN CT11997 10m - KP - 03/17

more style.
more function.
more radiant.

designed to be better.™





TABLE OF CONTENTS

02 **INTRO TO THE RADIANT COLLECTION**
• Design Inspiration
• Product Overview



16 **DIMMERS & FAN CONTROLS**



18 **SWITCHES, SENSORS & TIMERS**



22 **OUTLETS & USB CHARGING SOLUTIONS**



26 **RF LIGHTING SYSTEMS**



28 **SCREWLESS WALL PLATES**

Everyone wants a home that's a step above ordinary.

Now the radiant® collection of switches, outlets, dimmers and home automation controls by Legrand puts that stylish finishing touch affordably within reach. radiant gets rid of unsightly screws, delivering clean looks in a range of colors and metallic finishes. Put more modern convenience at your fingertips. Go more radiant.



Dimmers & Switches



TRU-UNIVERSAL DIMMER | RH703PTUW

The simplest solution to every dimming need, this dimmer self-calibrates to work with all dimmable lighting types and loads (except 0-10V). White LED enables easy location in the dark.

MULTI-LOCATION MASTER DIMMER | HCL453PMMW

This CFL/LED multi-location dimmer allows dimming from multiple locations.



SINGLE POLE COMBINATION SWITCH | RCD11W

The clean look of radiant hits home in this handsome combination switch. Two single pole switches tuck neatly into a single wall plate, delivering convenience without the clutter.

Outlets



TAMPER-RESISTANT OUTLET | 885TRW
It's safety first with a patented shutter system designed to prevent insertion of foreign objects. This outlet meets NEC® tamper-resistant requirements.

SELF-TEST GFCI OUTLET | 1597TRW
The utmost in protection, this new GFCI unit tests itself every three seconds to exceed the very latest industry standards for GFCI safety.



SINGLE POLE/3-WAY SWITCH/TAMPER-RESISTANT OUTLET COMBINATION | RCD38TRW
Fit two devices neatly into the footprint of one with this combination single pole/3-way switch and tamper-resistant outlet.

Night Lights



FULL LED NIGHT LIGHT | NTLFULLW
Energy-efficient soft-glow LED features five adjustable brightness levels and optional louver (shown in center image) for greater control. Shown with included optional louver.



NIGHT LIGHT WITH TAMPER-RESISTANT OUTLET | NTL885TRW
This seamlessly integrated night light features five adjustable brightness levels, an optional louver for greater light control and a hidden sensor that turns light on in the dark, off in daylight.

USB Charging Solutions



USB CHARGER WITH TAMPER-RESISTANT OUTLET | TM826USBW
Standard power meets modern convenience with this clever integration of two USB charging outlets, which provide 3.1 amps of combined charging power right alongside standard outlets.

QUAD USB CHARGER | TM8USB4W
radiant® USB charging solutions let you charge more of your devices without the need for bulky AC adapters. Charge up to four devices simultaneously with 4.2 Amps of total charging capacity.

RF Lighting Control



RF SCENE CONTROLLER | LC2303-WH
The Scene Controller is an in-wall keypad that pairs with the LC7001 Whole House Lighting Controller and installed RF Lighting Control devices to trigger preconfigured lighting scenes.





RF TRU-UNIVERSAL DIMMER | LC2101-WH
The RF Tru-Universal Dimmer operates all dimmable lighting types and loads (up to 700W), no control wiring necessary (except 0-10V).



RF REMOTE DIMMER | LC2103-WH
The RF Remote Dimmer operates all dimmable lighting types and loads (up to 700W), no control wiring necessary.

DIMMERS





Conveniently conserve energy and create the perfect mood by adjusting dimmer light levels with a single slide.

NAME	CATALOG NUMBER	COLOR/FINISH	AMP.	VAC	WATTS
Incandescent Single Pole/3-Way Dimmer 	RH1103PTC RH1103PW	Tri-Color White	15	120	1100W
Incandescent Single Pole/3-Way Dimmer 	RH703PW RH703PTC	Tri-Color White		120	700W
0-10V LED/Fluorescent Dimmer 	RH4FBL3PTC RH4FBL3PW	Tri-Color White	10	120	
Tru-Universal Single Pole/3-Way Dimmer 	RH703PTUTC RH703PTUW	Tri-Color White		120V, 60Hz	Incandescent, Halogen & ELV: 700W MLV: 500VA LED/CFL: 450W EFL: 5.5A

Note: Wall plates sold separately.

Tri-color includes: White, Light Almond and Ivory.

DIMMERS





NAME	CATALOG NUMBER	COLOR/FINISH	AMP.	VAC	WATTS
CFL/LED Dimmer (Not intended for electronic low voltage loads) 	RHCL453PTC RHCL453PW	Tri-Color White		120 VAC, 60 Hz	450W CFL/LED; 700W Incandescent
Magnetic Low-Voltage Single Pole/3-Way Dimmer 	RHLV1103PTC RHLV1103PW	Tri-Color White		120	1100W
Magnetic Low-Voltage Single Pole/3-Way Dimmer 	RHLV703PTC RHLV703PW	Tri-Color White		120	700W
2-Wire Fluorescent Dimmer 	RHFB83PTC RHFB83PW	Tri-Color White	8	120	

Note: Wall plates sold separately.

Tri-color includes: White, Light Almond and Ivory.

MULTI-LOCATION DIMMERS


Conveniently conserve energy and create the perfect mood by adjusting dimmer light levels with a single slide.

NAME	CATALOG NUMBER	COLOR/FINISH	AMP.	VAC	NEMA CONFIG NUMBER
Multi-Location Master Dimmer 	HCL453PMMTC HCL453PMMW	Tri-Color White		120, 60Hz	5-15R 700W Incandescent
Interchangeable Face Cover for Multi-Location Master Dimmer 	HMKIT HMKITBK HMKITDB HMKITGRY HMKITI HMKITLA HMKITNI HMKITW	Brown Black Dark Bronze Gray Ivory Light Almond Nickel White			
Multi-Location Remote Dimmer 	HMRTC HMRW	Tri-Color White		120, 60Hz	
Interchangeable Face Cover for Multi-Location Remote Dimmer 	HMRKIT HMRKITBK HMRKITDB HMRKITGRY HMRKITI HMRKITLA HMRKITNI HMRKITW	Brown Black Dark Bronze Gray Ivory Light Almond Nickel White			





Note: Wall plates sold separately.
Tri-color includes: White, Light Almond and Ivory.

DIMMER ACCESSORIES

NAME	CATALOG NUMBER	COLOR/FINISH	AMP.	VAC	NOTE
Interchangeable Face Cover 	RHKIT RHKITBK RHKITDB RHKITGRY RHKITI RHKITLA RHKITNI RHKITW	Brown Black Dark Bronze Gray Ivory Light Almond Nickel White			Applies to all dimmers on pages 14 & 15

FAN CONTROLS

NAME	CATALOG NUMBER	COLOR/FINISH	AMP.	VAC	NOTE
Fan Speed Control De-Hummer, Single Pole/3-Way 	RHDH163PTC	Tri-Color	1.6A	120V	
Fan Speed Control De-Hummer, Single Pole/3-Way 	RHDH163PW	White	1.6A	120V	

SWITCHES

Modern low-profile paddle switches with no screws in sight.

NAME	CATALOG NUMBER	COLOR/FINISH	AMP.	VAC	NEMA CONFIG NUMBER
15A Single Pole Switch*	TM870 TM870BK TM870DBCC10 TM870GRY TM870I TM870ISL (lighted) TM870LA TM870LASL (lighted) TM870NICC10 TM870W TM870WSL (lighted)	Brown Black Dark Bronze Gray Ivory Ivory Light Almond Light Almond Nickel White White	15	120	
3-Way Switch*	TM873 TM873BK TM873DBCC10 TM873GRY TM873I TM873ISL (lighted) TM873LA TM873LASL (lighted) TM873NICC10 TM873W TM873WSL (lighted)	Brown Black Dark Bronze Gray Ivory Ivory Light Almond Light Almond Nickel White White	15	120	
15A 4-Way Switch	TM874 TM874BK TM874DBCC6 TM874I TM874ISL (lighted) TM874LA TM874LASL (lighted) TM874NICC6 TM874W TM874WSL (lighted)	Brown Black Dark Bronze Ivory Ivory Light Almond Light Almond Nickel White White	15	120	

* These switches are identical

Note: Wall plates sold separately.



COMBINATION SWITCHES

NAME	CATALOG NUMBER	COLOR/FINISH	AMP.	VAC	NEMA CONFIG NUMBER
Two Single Pole Switches & Single Pole/3-Way Switch	RCD113 RCD113BK RCD113I RCD113LA RCD113W	Brown Black Ivory Light Almond White	15	120/125	
Two Single-Pole Switches	RCD11 RCD11BKCC6 RCD11I RCD11LA RCD11W	Brown Black Ivory Light Almond White	15	120/125	
Two Single Pole/3-Way Switches*	RCD33BK RCD33I RCD33LA RCD33W	Black Ivory Light Almond White	15	120/125	
Single Pole/3-Way Switch & Tamper-Resistant Single Receptacle*	RCD38TRBK RCD38TRI RCD38TRLA RCD38TRW	Black Ivory Light Almond White	15	120/125	5-15R
Locator Light Module	RCDLM	NA			

* These switches are identical


Note: Wall plates sold separately.

SENSORS

NAME	CATALOG NUMBER	COLOR/FINISH	AMP.	VAC	NEMA CONFIG NUMBER
120V Single Pole/3-Way Occupancy Sensor 	RRW600UTC	Tri-Color		120	
120V Single Pole Vacancy Sensor 	RRW600VTC	Tri-Color		120	



TIMERS

NAME	CATALOG NUMBER	COLOR/FINISH	AMP.	VAC	NEMA CONFIG NUMBER
4-Button Digital Timer 	RT2BK RT2I RT2LA RT2W	Black Ivory Light Almond White		120	






Note: Wall plates sold separately.



Tri-color includes: White, Light Almond and Ivory.

OUTLETS





Not all outlets are created equal. While some simply deliver power, others protect against electrical shock and fire.

NAME	CATALOG NUMBER	COLOR/FINISH	AMP.	VAC	NEMA CONFIG NUMBER
 Tamper-Resistant Receptacle	885TR 885TRBK 885TRDBCC12 885TRGRY 885TRI 885TRLA 885TRNICC12 885TRW	Brown Black Dark Bronze Gray Ivory Light Almond Nickel White	15	120/125	5-15R
 Weather-Resistant Receptacle	885TRWR 885TRWRI 885TRWRLA 885TRWRW	Brown Ivory Light Almond White	15	125	5-15R
 Tamper-Resistant Spec Grade Receptacle	TR26352R TR26352RBK TR26352RGRY TR26352RI TR26352RLA TR26352RW	Brown Black Gray Ivory Light Almond White	20	125	5-20R

USB CHARGING SOLUTIONS

NAME	CATALOG NUMBER	COLOR/FINISH	AMP.	VAC	NEMA CONFIG NUMBER
 USB Chargers with Duplex 15A Tamper-Resistant Outlets	TM826USBBK TM826USBI TM826USBLA TM826USBNICC6 TM826USBW	Black Ivory Light Almond Nickel White	15	120	3.1 Amp
 Quad USB Charger	TM8USB4BKCC6 TM8USB4ICC6 TM8USB4LACC6 TM8USB4NICC6 TM8USB4WCC6	Black Ivory Light Almond Nickel White		125	4.2 Amp





NIGHT LIGHTS

NAME	CATALOG NUMBER	COLOR/FINISH	AMP.	VAC	NEMA CONFIG NUMBER
 Night Light with Two 15A Tamper-Resistant Outlets	NTL885TRBKCC6 NTL885TRICC6 NTL885TRLACC6 NTL885TRNICC6 NTL885TRW	Black Ivory Light Almond Nickel White	15	120/125	5-15R
 Night Light With Single-Pole, 3-Way Switch	NTL873BKCC6 NTL873ICC6 NTL873LACC6 NTL873NICC6 NTL873WCC6	Black Ivory Light Almond Nickel White	15	120/125	
 Full Night Light with Adjustable Light Levels (An optional louver is included for added light-level control)	NTLFULLTC NTLFULLW	Tri-Color White		120/125	
 Horizontal Step Light	NTLHORZTCCC6 NTLHORZWCC6	Tri-Color White		120/125	




Note: Wall plates sold separately.

Tri-color includes: Light Almond, Ivory and Black.

GFCI

NAME	CATALOG NUMBER	COLOR/FINISH	AMP	VAC	NEMA CONFIG NUMBER
Combination Tamper-Resistant 15A Self-Test Night Light/GFCI 	1597NLTTRBKCC4 1597NLTTRDBCC4 1597NLTTRI 1597NLTTRLA 1597NLTTRNICC4 1597NLTTRW	Black Gray Ivory Light Almond Nickel White	15	125	5-15R
Combination Tamper-Resistant 15A Self-Test Single-Pole Switch/GFCI 	1597SWTTRBKCC4 1597SWTTRICC4 1597SWTTRLACC4 1597SWTTRWCC4	Black Ivory Light Almond White	15	125	5-15R
Tamper-Resistant 20A Self-Test Duplex GFCI 	2097TR 2097TRBK 2097TRGRY 2097TRI 2097TRLA 2097TRW	Brown Black Gray Ivory Light Almond White	20	125	5-20R
Combination Tamper-Resistant 20A Self-Test Night Light/GFCI 	2097NLTTRGRY 2097NLTTRI 2097NLTTRLA 2097NLTTRW	Gray Ivory Light Almond White	20	125	5-20R

GFCI

NAME	CATALOG NUMBER	COLOR/FINISH	AMP	VAC	NEMA CONFIG NUMBER
Spec-Grade Tamper-Resistant 15A Self-Test Duplex GFCI 	1597TR 1597TRBK 1597TRDBCC4 1597TRGRY 1597TRI 1597TRLA 1597TRNICC4 1597TRW	Brown Black Dark Bronze Gray Ivory Light Almond Nickel White	15	125	5-15R
Audible Alarm Tamper-Resistant 15A Self-Test Duplex GFCI 	1597TRA 1597TRABK 1597TRAI 1597TRALA 1597TRAW	Brown Black Ivory Light Almond White	15	125	5-15R
Spec-Grade Weather-Resistant 15A Self-Test Duplex GFCI 	1597TRWR 1597TRWRBK 1597TRWRGRY 1597TRWRI 1597TRWRLA 1597TRWRW	Brown Black Gray Ivory Light Almond White	15	125	5-15R



Note: Wall plates sold separately.

RF DIMMERS & SWITCHES

Easy management for dimmers, switches, and other devices allows users to adjust lighting with effortless precision. Whether shedding more light on some fine print or dimming things down for movie time, with radiant® RF Lighting Control you can ensure customers always have the best light for the task at hand while even providing energy savings.

NAME	CATALOG NUMBER	COLOR/FINISH	AMP	VAC	NOTE
RF Tru-Universal Master Dimmer 	LC2101-LA LC2101-NI LC2101-WH	Light Almond Nickel White		120	NOTE: 1-GANG LOAD RATING 700W, DERATED TO 600W IN 2-GANG AND 500W IN 3-GANG
RF 2-Wire Incandescent Master Dimmer 	LC2102-LA LC2102-NI LC2102-WH	Light Almond Nickel White		120	NOTE: 1-GANG LOAD RATING 600W, DERATED TO 500W IN 2-GANG AND 400W IN 3-GANG
RF Remote Dimmer 	LC2103-LA LC2103-NI LC2103-WH	Light Almond Nickel White		120	
RF 1500W Master Switch 	LC2201-LA LC2201-NI LC2201-WH	Light Almond Nickel White		120	
RF Remote Switch 	LC2203-LA LC2203-NI LC2203-WH	Light Almond Nickel White		120	

Note: Wall plates sold separately.



DOWNLOAD THE LEGRAND LIGHTING CONTROL APP

Convenient control of your lighting from the intuitive app available for Android and iOS smartphones and tablets.










RF LIGHTING CONTROL

NAME	CATALOG NUMBER	COLOR/FINISH	MAX LOAD	NOTE
RF Scene Controller 	LC2303-LA LC2303-NI LC2303-WH	Light Almond Nickel White		
Plug-In RF Tru-Universal Lamp Module 	LC2150	White	300W Incandescent 300W ELV 200W CFL 200W LED	
The Hub 	LC7001	Black		The Hub works in conjunction with the Legrand Lighting Control iOS and Android app to enable control and automation for all Legrand RF Lighting Control devices through smartphones and tablets.
RS232 to RF Interface 	MR232-G	Black		Enables integration of a third party control system with the Whole-House Lighting System. Features a two-wire interface from other control systems and two operating modes (maintained or momentary type inputs). Includes power supply.
Repeater & Away Emulator 	MRR2-G	Black		Provides extra security when you're on vacation. Records the normal usage of lights throughout a 24-hour period and then plays them back when you're not at home. Also expands the range of the system from 100' to 300'.
In-Wall 2000W Box Dimmer 	MR2000	Black		Supports the addition of large lighting loads (up to 2000W) to the RF Lighting System.
Plug-In Small Appliance Module 	MRP7-W	White		Allows remote control of small appliances such as coffeemakers, radios, and TVs when used with the RF Lighting System. Simply plug the module into any grounded, 120V outlet and then plug the appliance into the module.



Note: Wall plates sold separately.

SCREWLESS WALL PLATES

How to build a better wall plate? Try clean lines and a low profile with no screws in sight.


NAME	GANGS	PART NUMBER	NAME	GANGS	PART NUMBER
Black 	1-Gang	RWP26BK	Ivory 	1-Gang	RWP26I
	2-Gang	RWP262BK		2-Gang	RWP262I
	3-Gang	RWP263BK		3-Gang	RWP263I
	4-Gang	RWP264BK		4-Gang	RWP264I
	5-Gang	RWP265BK		5-Gang	RWP265I
	6-Gang	RWP266BK		6-Gang	RWP266I
Brown 	1-Gang	RWP26	Light Almond 	1-Gang	RWP26LA
	2-Gang	RWP262		2-Gang	RWP262LA
	3-Gang	RWP263		3-Gang	RWP263LA
	4-Gang	RWP264		4-Gang	RWP264LA
	5-Gang	RWP265		5-Gang	RWP265LA
	6-Gang	RWP266		6-Gang	RWP266LA
Grey 	1-Gang	RWP26GRY	White 	1-Gang	RWP26W
	2-Gang	RWP262GRY		2-Gang	RWP262W
	3-Gang	RWP263GRY		3-Gang	RWP263W
	4-Gang	RWP264GRY		4-Gang	RWP264W
	5-Gang	RWP265GRY		5-Gang	RWP265W
	6-Gang	RWP266GRY		6-Gang	RWP266W

METALLIC SCREWLESS WALL PLATES

NAME	GANGS	PART NUMBER	NAME	GANGS	PART NUMBER
Dark Bronze 	1-Gang	RWP26DBCC6	Nickel 	1-Gang	RWP26NICC6
	2-Gang	RWP262DBCC6		2-Gang	RWP262NICC6
	3-Gang	RWP263DBCC6		3-Gang	RWP263NICC6
	4-Gang	RWP264DB		4-Gang	RWP264NI
	5-Gang	RWP265DB		5-Gang	RWP265NI
	6-Gang	RWP266DB		6-Gang	RWP266NI



radiant layers on the style with tasteful color and metallic finish options to coordinate with any decor. radiant screwless wall plates (sold separately) are available in up to six-gang options.



PART NO.	PAGE NO.	PART NO.	PAGE NO.
Symbols		2097TRGRY	24
885TRDBCC12	22	2097TRI	24
885TRGRY	22	2097TRLA	24
885TRI	22	2097TRW	24
885TRLA	22		
885TRNICC12	22	H	
885TRW	6, 22	HCL453PMMTC	16
885TRWR	22	HCL453PMMW	4, 16
885TRWRI	22	HMKIT	16
885TRWRLA	22	HMKITBK	16
885TRWRW	22	HMKITDB	16
885W	22	HMKITGRY	16
1597NTLTRBKCC4	24	HMKITI	16
1597NTLTRDBCC4	24	HMKITLA	16
1597NTLTRICC4	24	HMKITNI	16
1597NTLTRLACC4	24	HMKITW	16
1597NTLTRNICC4	24	HMRKIT	16
1597NTLTRWCC4	24	HMRKITBK	16
1597SWTTRBKCC4	24	HMRKITDB	16
1597SWTTRICC4	24	HMRKITGRY	16
1597SWTTRLACC4	24	HMRKITI	16
1597SWTTRWCC4	24	HMRKITLA	16
1597TR	25	HMRKITNI	16
1597TRA	25	HMRKITW	16
1597TRABK	25	HMRTC	16
1597TRAI	25	HMRW	16
1597TRALA	25		
1597TRAW	25	L	
1597TRBK	25	LC2101-LA	26
1597TRDBCC4	25	LC2101-NI	26
1597TRGRY	25	LC2101-WH	12, 26
1597TRI	25	LC2102-LA	26
1597TRLA	25	LC2102-NI	26
1597TRNICC4	25	LC2102-WH	26
1597TRW	6, 25	LC2103-LA	26
1597TRWR	25	LC2103-NI	26
1597TRWRBK	25	LC2103-WH	13, 26
1597TRWRGRY	25	LC2150	27
1597TRWRI	25	LC2201-LA	26
1597TRWRLA	25	LC2201-NI	26
1597TRWRW	25	LC2201-WH	26
1597W	24	LC2203-LA	26, 27
2097NTLTRGRY	24	LC2203-NI	26
2097NTLTRI	24	LC2203-WH	26
2097NTLTRLA	24	LC2303-LA	27
2097NTLTRW	24	LC2303-NI	27
2097TR	24	LC2303-WH	12, 27
2097TRBK	24	LC7001	27

PART NO.	PAGE NO.	PART NO.	PAGE NO.
M		N	
MR232-G	27	NTL873BKCC6	23
MR2000	27	NTL873ICC6	23
MRP7-W	27	NTL873LACC6	23
MRR2-G	27	NTL873NICC6	23
		NTL873WCC6	23
		NTL885TRBKCC6	23
		NTL885TRICC6	23
		NTL885TRLACC6	23
		NTL885TRNICC6	23
		NTL885TRW	9, 23
		NTL885TRWCC6	9, 23
		NTLFULLTC	23
		NTLFULLTCCC6	23
		NTLFULLW	8, 23
		NTLFULLWCC6	8, 23
		NTLHORZTCCC6	23
		NTLHORZWCC6	23
		R	
		RCD11BKCC6	19
		RCD11DBCC6	19
		RCD11I	19
		RCD11LA	19
		RCD11NICC6	19
		RCD11W	5, 19
		RCD33BK	19
		RCD33DBCC6	19
		RCD33I	19
		RCD33LA	19
		RCD33NICC6	19
		RCD33W	19
		RCD38TRBK	19
		RCD38TRDBCC6	19
		RCD38TRI	19
		RCD38TRLA	19
		RCD38TRNICC6	19
		RCD38TRW	7, 19
		RCD113BK	19
		RCD113DBCC6	19
		RCD113I	19
		RCD113LA	19

PART NO.	PAGE NO.	PART NO.	PAGE NO.	PART NO.	PAGE NO.
RCD113NICC6	19	RWP262W	28	TM826USBWCC6	10, 22
RCD113W	19	RWP263	28	TM870	18
RCDLM	19	RWP263BK	28	TM870BK	18
RH4FBL3PTC	14	RWP263DBCC6	28	TM870DBCC10	18
RH4FBL3PW	14	RWP263GRY	28	TM870GRY	18
RH703PTC	14	RWP263I	28	TM870I	18
RH703PTUTC	14	RWP263LA	28	TM870ISL	18
RH703PTUW	4, 14	RWP263NICC6	28	TM870LA	18
RH703PW	14	RWP263W	28	TM870LASL	18
RH1103PTC	14	RWP264	28	TM870NICC10	18
RH1103PW	14	RWP264BK	28	TM870W	18
RHCL453PTC	15	RWP264DB	28	TM870WSL	18
RHCL453PW	15	RWP264GRY	28	TM873	18
RHDH163PTC	17	RWP264I	28	TM873BK	18
RHDH163PW	17	RWP264LA	28	TM873DBCC10	18
RHFB83PTC	15	RWP264NI	28	TM873GRY	18
RHFB83PW	15	RWP264W	28	TM873I	18
RHKIT	17	RWP265	28	TM873ISL	18
RHKITBK	17	RWP265BK	28	TM873LA	18
RHKITDB	17	RWP265DB	28	TM873LASL	18
RHKITGRY	17	RWP265GRY	28	TM873NICC10	18
RHKITI	17	RWP265I	28	TM873W	18
RHKITLA	17	RWP265LA	28	TM873WSL	18
RHKITNI	17	RWP265NI	28	TM874	18
RHKITW	17	RWP265W	28	TM874ABCC6	18
RHLV703PTC	15	RWP266	28	TM874BK	18
RHLV703PW	15	RWP266BK	28	TM874DBCC6	18
RHLV1103PTC	15	RWP266DB	28	TM874I	18
RHLV1103PW	15	RWP266GRY	28	TM874ISL	18
RRW600UTC	20	RWP266I	28	TM874LA	18
RRW600VTC	20	RWP266LA	28	TM874LASL	18
RT2BK	20	RWP266NI	28	TM874NICC6	18
RT2I	20	RWP266W	28	TM874W	18
RT2LA	20			TM874WSL	18
RT2W	20	T		TR26352R	22
RWP26	28	TM8USB4BKCC6	22	TR26352RBK	22
RWP26BK	28	TM8USB4ICC6	22	TR26352RGRY	22
RWP26DBCC6	28	TM8USB4LACC6	22	TR26352RI	22
RWP26GRY	28	TM8USB4NICC6	22	TR26352RLA	22
RWP26I	28	TM8USB4W	10	TR26352RW	22
RWP26LA	28	TM8USB4WCC6	22		
RWP26NICC6	28	TM826USBBK	22		
RWP26W	28	TM826USBBKCC6	22		
RWP262	28	TM826USBI	22		
RWP262BK	28	TM826USBICC6	22		
RWP262DBCC6	28	TM826USBLA	22		
RWP262GRY	28	TM826USBLACC6	22		
RWP262I	28	TM826USBNICC6	22		
RWP262LA	28	TM826USBW	10, 22		
RWP262NICC6	28				

