



Shown: p5644-20-30K, Square Outdoor

2017 CALIFORNIA TITLE 24 BROCHURE

 **PROGRESS**
LIGHTING™

CALIFORNIA TITLE 24

QUALITY
FUNCTIONALITY
SUPERIOR PERFORMANCE



Title 24 is enforced by the building or electrical inspector at the site of the lighting installation and may involve the homeowner, contractor and/or builder. The building permit process is used to identify and track compliance. If a lighting installation is non-compliant as installed, an occupancy permit may be delayed or denied. Use this guide to select T-24 compliant products for your next project.



WHAT HAS CHANGED SINCE TITLE 24 2013?

ALL HIGH EFFICACY LIGHTING

Indoor and outdoor lighting for new homes must be high efficacy.

SIMPLIFIED CONTROL REQUIREMENTS

Lighting control requirements for indoor spaces are now simpler. Control requirements are based, in nearly all cases, on the type of lamp or luminaire installed, not the space.

JA8 UPDATED

Joint Appendix 8 defines the performance requirements for high efficacy LED sources and requires that LED sources provide 90+ CRI illumination and a R9 value of ≥ 50 (both of these metrics equate to lighting that is more pleasing in residential applications). LED sources must also now meet strict requirements for reduced flicker, $< 30\%$ both at 100% and when dimmed to 20%.

HOW DO I KNOW WHICH PRODUCTS MEET TITLE 24 2016?

HIGH EFFICACY LED, MEETS JA8-2016



Any fixture with a **screw base socket** complies with Title 24 when a **JA8 listed light bulb** is installed. The light bulb must be marked either as: JA8-2016 or JA8-2016-E. The E indicates the bulb has been tested and meets requirements established for use in enclosed fixtures (ex: flush mounts).

**Note: Recessed downlights may not have a screw base socket regardless of lamp type.*



Any fixture that has an **Integrated LED** that has been tested and listed in the California Appliance Database. Check for certified bulbs or fixtures by searching the MAEDBS database. Go to: cacertappliances.energy.ca.gov


HIGH EFFICACY LED, NOT REQUIRED TO MEET JA8



Table 150.0A defines products that do not have to meet JA8, the most common types include:

- Pin-based linear or compact fluorescent light sources using electronic ballasts
- GU-24 sockets containing light sources other than LEDs
- Inseperable SSL luminaires that are installed outdoors

TERMS & REQUIREMENTS



OUTDOOR CONTROLS

For single family homes, lighting mounted to a building must be controlled by one of the combinations: Photocell and motion sensor, photocell and time switch, astronomical time clock or EMCS with features of astronomical time clock, that does not allow the luminaire to be ON during the day, and may be programmed to automatically turn lighting OFF at night.


RECESSED LIGHTING

Recessed Downlight housings must be rated for direct contact with insulation (Type IC), as well as be labeled and certified airtight with air leakage less than 2.0 CFM at 75 Pascals when tested with accordance with ASTM E283. The opening must be sealed with a gasket or caulk between the housing and ceiling. The recessed housing shall not contain a screw based socket. In addition, the light source must be high efficacy and comply with Reference Joint Appendix JA8. It must also be marked "JA8-2016".



CONSTRUCTION & INSPECTION

The builder must now provide new homeowners with a schedule that includes a list of installed lamps and luminaires.



CONTROL REQUIREMENTS BY SPACE

At least one luminaire in the bathroom, garage, laundry room and utility room must be controlled by a vacancy sensor. Preset scene controllers and EMCS can take the place of dimmers as long as the functionality meets code requirements.



SCREW-BASE LUMINAIRES

All luminaires that utilize a screw-based socket must contain lamps that comply with JA8 high efficacy requirements. All enclosed, screw-base luminaires, must utilize a compliant lamp rated for elevated temperatures.




HIGH EFFICACY LIGHTING

Per Table 150.0 A, fixtures with a GU-24 socket and compact fluorescent lamp or an inseparable LED source are not required to meet JA8.

TABLE OF CONTENTS

Recessed & Surface Mount 6-10



Close-to-Ceiling 11-18



Ceiling Fans & Light Kits 19-22



Bath 23-25



Outdoor 26-57



Sconces 58-60



Chandelier & Pendants 61-63



Pictorial Index 64-75



Shown: Recessed Lighting

Recessed & Surface Mount

RECESSED LIGHTING

Progress Lighting offers LED recessed retrofit solutions that are ideal for residential applications. The retrofit family offers a convenient way to upgrade to LED lighting with a quick push and twist installation, while providing up to a 75% energy savings. The retrofit LED family features smooth dimming down to 10% using Triac / Forward Phase dimming.

4" LED

LED HOUSING



P831-LED

Ceiling opening: 4-1/2"
Plaster frame: 8-3/8" x 13"
Recessed depth: 7-1/2"

- Integral quick link connector mates with P8080 and P8046 series LED trims
- New construction housing
- IC rated airtight

T24

4" LED TRIM

Flicker free dimming down to 10% with many Triac or forward phase dimmers. Flicker rate less than 30%.


P8080-09-30K Brushed Nickel

P8080-20-30K Antique Bronze

P8080-28-30K White

P8080-31-30K Black

One integral 9.5w LED module included.
630 lumens, 66 lumens per watt.



P8080-09-30K



P8080-20-30K



P8080-28-30K



P8080-31-30K

P8080 & P8046 FEATURES

- Frosted polycarbonate lens controls direct glare from LEDs
- Lumen output and distribution comparable to 50w R20 incandescent lamp
- CRI is 90+
- 50,000 hours life based on 70% lumen maintenance (TM-21)
- Suitable for use in IC or NON-IC applications
- cULus listed for wet locations
- Triac/forward phase dimming

4" EYE BALL

Flicker free dimming down to 10% with many Triac or forward phase dimmers. Flicker rate less than 30%.

P8046-09-30K Brushed Nickel

P8046-20-30K Antique Bronze

P8046-28-30K White

P8046-31-30K Black

One integral 9.5w LED module included.
630 lumens, 66 lumens per watt.
Triac/forward phase dimming.



P8046-09-30K



P8046-20-30K



P8046-28-30K



P8046-31-30K



Shown: Recessed Lighting
(Image: Vicki Payne)

5" LED

LED HOUSING



P84-LED

Ceiling opening: 5-1/4"
Plaster frame: 7-7/8" x 10-3/4"
Recessed depth: 5-1/2"

- Integral quick connectors mate with P8061 and P8176 series
- New construction housing
- IC rated airtight

T24

5" LED TRIM

Flicker free dimming down to 10% with many Triac or forward phase dimmers. Flicker rate less than 30%.

P8061-09-30K Brushed Nickel
P8061-20-30K Antique Bronze
P8061-28-30K White
P8061-31-30K Black
One integral 10.5w LED module included.
700 lumens, 66 lumens per watt.



P8061-09-30K



P8061-20-30K



P8061-28-30K



P8061-31-30K

P8061 & P8176 FEATURES

- Frosted polycarbonate lens controls direct glare from LEDs
- Lumen output and distribution comparable to 65w BR30 incandescent lamp
- CRI is 90+ rivaling CFL
- 50,000 hours life based on 70% lumen maintenance (TM-21)
- Suitable for use in IC or NON-IC applications
- cULus listed for wet locations
- Triac/forward phase dimming

5" EYE BALL

Flicker free dimming down to 10% with many Triac or forward phase dimmers. Flicker rate less than 30%.

P8176-09-30K Brushed Nickel
P8176-20-30K Antique Bronze
P8176-28-30K White
P8176-31-30K Black
One integral 10.5w LED module included.
670 lumens, 63 lumens per watt.
Triac/forward phase dimming.



P8176-09-30K



P8176-20-30K



P8176-28-30K



P8176-31-30K

6" LED

LED HOUSING



P87-LED

Ceiling opening: 6-7/8" dia.
Plaster frame: 7-7/8" x 10-3/4"
Recessed depth: 7-1/2"
Pryouts: 1/2" & 3/4"

- Integral quick connect mates with P8071 and P8076 series LED trims.
- New construction housing
- IC rated airtight

T24

6" EYE BALL

Flicker free dimming down to 10% with many Triac or forward phase dimmers. Flicker rate less than 30%.

P8076-09-30K Brushed Nickel
P8076-20-30K Antique Bronze
P8076-28-30K White
P8076-31-30K Black
One integral 10.5w LED module included.
700 lumens, 66 lumens per watt.
Triac/forward phase dimming.



P8076-09-30K



P8076-20-30K



P8076-28-30K



P8076-31-30K

6" LED TRIM - TRIAC DIMMING

Flicker free dimming with Triac or forward phase dimmers. Flicker rate less than 30%.

P8071-09-30K Brushed Nickel
P8071-20-30K Antique Bronze
P8071-28-30K White
P8071-31-30K Black
One integral 10.5w LED module included.
725 lumens, 69 lumens per watt.




P8071-20-30K



P8071-28-30K



P8071-31-30K



P8071-09-30K

P8071 & P8076 FEATURES

- Frosted polycarbonate lens controls direct glare from the LEDs
- Lumen output and distribution comparable to a 65w BR30 incandescent lamp
- 3000K color temperature
- 90+ CRI
- TM-21 50,000 hours life
- Suitable for use in IC or NON-IC applications
- CSAus listed for wet locations

LED SURFACE MOUNT

5-1/2" ROUND

Flicker free dimming down to 10% with many Triac or forward phase dimmers. Flicker rate less than 30%.

P8240-20-30K Antique Bronze

P8240-28-30K White

P8240-31-30K Black

P8240-82-30K Metallic Gray

5-1/2" Round flush mount

5-1/2" dia., 1-1/2" ht.

One integral 10.5w LED module included.

660 lumens, 62 lumens per watt.

Triac/forward phase dimming.



P8240-20-30K



P8240-28-30K



P8240-31-30K



P8240-82-30K



5-1/2" SQUARE

Flicker free dimming down to 10% with many Triac or forward phase dimmers. Flicker rate less than 30%.

P8241-20-30K Antique Bronze

P8241-28-30K White

P8241-31-30K Black

P8241-82-30K Metallic Gray

5-1/2" Square flush mount

5-1/2" sq., 1-1/2" ht.

One integral 10.5w LED module included.

645 lumens, 61 lumens per watt.

Triac/forward phase dimming.



P8241-20-30K



P8241-28-30K



P8241-31-30K



P8241-82-30K



5-1/2" DECORATIVE ROUND

Flicker free dimming down to 10% with many Triac or forward phase dimmers. Flicker rate less than 30%.

P8247-09-30K Brushed Nickel

P8247-20-30K Antique Bronze

P8247-28-30K White

P8247-31-30K Black

Round with etched glass

5-1/2" round, 1-1/2" ht.

One integral 10.5w LED module included.

690 lumens, 66 lumens per watt.

Triac/forward phase dimming.



P8247-09-30K



P8247-20-30K



P8247-28-30K



P8247-31-30K



LED SURFACE MOUNT

5-1/2" SLIM-LINE

Flush mount that can mount into a minimum 2" deep J-box. For list of compatible J-boxes see spec sheet.

LED SLIM-LINE SURFACE MOUNT

P8108-20-30K Antique Bronze

P8108-28-30K White

P8108-31-30K Black

P8108-82-30K Metallic Gray

5-1/2" dia., 2-3/4" ht.

One 11.75w LED module included.

685 lumens, 58 lumens per watt.

Triac/forward phase dimming.



P8108-28-30K



7-1/4" ROUND

Flicker free dimming down to 10% with many Triac or forward phase dimmers. Flicker rate less than 30%.

P8022-20-30K Antique Bronze

P8022-28-30K White

P8022-31-30K Black

P8022-82-30K Metallic Gray

7-1/4" round flush mount/recessed.

7-1/4" dia., 1-1/4" ht.

One 17W LED module.

Triac/forward phase dimming.



P8022-20-30K



P8022-28-30K



P8022-31-30K



P8022-82-30K



P8222-28-30K White

7-1/4" round flush mount

7-1/4" dia., 1-1/4" ht.

One 17W LED module.



P8222-28-30K



7-1/4" DECORATIVE ROUND

Flicker free dimming down to 10% with many Triac or forward phase dimmers. Flicker rate less than 30%.

P8147-09-30K Brushed Nickel

P8147-20-30K Antique Bronze

P8147-28-30K White

P8147-31-30K Black

Round trim with etched glass

7-1/4" dia., 2-3/4" ht.

One 17W LED module.

Triac/forward phase dimming.



P8147-09-30K



P8147-20-30K



P8147-28-30K



P8147-31-30K













Shown: P3925-09EB Close-to-Ceiling
(Image: Eastwood Homes)

Close-to-Ceiling

LED SQUARE GLASS

PRODUCT NO.	FINISH	DESCRIPTION	SIZE	LAMP(S)	
P350017-009-30	Brushed Nickel	One-light	9-1/2" sq.,	1 17w LED module included	 
P350017-020-30	Antique Bronze	Swirl pattern glass	4-1/2" ht.	1452 source lumens, 90 CRI	
P350018-009-30	Brushed Nickel	One-light	11-3/8" sq.,	1 24w LED module included	 
P350018-020-30	Antique Bronze	Swirl pattern glass	5" ht.	2015 source lumens, 90 CRI	
P350019-009-30	Brushed Nickel	One-light	9-1/2" sq.,	1 17w LED module included	 
P350019-020-30	Antique Bronze	Alabaster glass	4-1/2" ht.	1452 source lumens, 90 CRI	
P350020-009-30	Brushed Nickel	One-light	11-3/8" sq.,	1 24w LED module included	 
P350020-020-30	Antique Bronze	Alabaster glass	5" ht.	2015 source lumens, 90 CRI	

LED FEATURES

- 120V AC replaceable module
- 3000K color temperature
- TM-21 60,000 hr. life
- Dimmable to 10% with Triac or ELV dimmers

PROGRESS **LED**



P350017-009-30



P350019-009-30



P350017-020-30



P350019-020-30



P350018-009-30



P350020-009-30











P350018-020-30



P350020-020-30

LED FLUSH

PRODUCT NO.	FINISH	DESCRIPTION	SIZE	LAMP(S)	
P350051-009-30	Brushed Nickel	One-light	11" dia.,	1 17w LED module included	 
P350051-020-30	Antique Bronze	Etched Glass	4-3/16" ht.	1452 source lumens, 90 CRI	
P350052-009-30	Brushed Nickel	One-light	12-9/16" dia.,	1 25w LED module included	 
P350052-020-30	Antique Bronze	Etched Glass	4-1/2" ht.	2015 source lumens, 90 CRI	
P350053-009-30	Brushed Nickel	One-light	11" dia.,	1 17w LED module included	 
P350053-020-30	Antique Bronze	Etched Glass	4" ht.	1452 source lumens, 90 CRI	
P350054-009-30	Brushed Nickel	One-light	13-1/4" dia.,	1 25w LED module included	 
P350054-020-30	Antique Bronze	Etched Glass	4-3/4" ht.	2015 source lumens, 90 CRI	

LED FEATURES

- 120V AC replaceable module
- 3000K color temperature
- TM-21 60,000 hr. life
- Dimmable to 10% with Triac or ELV dimmers

PROGRESS **LED**



P350051-009-30



P350052-009-30



P350053-009-30



P350054-009-30



P350051-020-30



P350052-020-30



P350053-020-30



P350054-020-30

INSPIRE

Off-white linen shade with diffuser.

LED SEMI-FLUSH MOUNT
P3683-0930K9 Brushed Nickel
P3683-2030K9 Antique Bronze
 13" dia., 10-5/8" ht.
 One 3000K 17w LED
 module included.
 1452 source lumens, 90 CRI.



P3683-2030K9



P3683-0930K9

LED FLUSH MOUNT
P3696-0930K9 Brushed Nickel
P3696-2030K9 Antique Bronze
 13" dia., 6" ht.
 One 3000K 17w LED
 module included.
 1452 source lumens, 90 CRI.



P3696-2030K9



P3696-0930K9



TWO-LIGHT CFL SEMI-FLUSH
P3939-09 Brushed Nickel
P3939-20 Antique Bronze
 White acrylic diffuser.
 13" dia., 10-1/2" ht.
 Two GU24 CFL lamps,
 each 26w max.



P3939-20



P3939-09

MELON GLASS GU24

Etched melon facet glass shades with metal trim and decorative knobs.
 Energy efficient lamps included.

PRODUCT NO.	FINISH	DESCRIPTION	SIZE	LAMP(S)
P3702-09WB	Brushed Nickel	One-light	11-3/8" dia., 6" ht.	1 13w GU24 included
P3703-09WB P3703-20WB P3703-30WB	Brushed Nickel Antique Bronze White	Two-light	13-1/4" dia., 7" ht.	2 13w GU24 included
P3704-09WB	Brushed Nickel	Three-light	15-1/4" dia., 7-1/2" ht.	3 13w GU24 included



P3702-09WB



P3704-09WB



P3703-20WB



P3703-09WB



P3703-30WB

ETCHED ALABASTER GLASS GU24

Smooth etched alabaster glass with metal trim. Energy efficient lamps included.

PRODUCT NO.	FINISH	DESCRIPTION	SIZE	LAMP(S)	
P3760-09EBWB	Brushed Nickel	Two-light	16-3/4" dia., 5-1/2" ht.	2 18w GU24 CFL included	T24
P3760-20EBWB	Antique Bronze				
P3764-09EBWB	Brushed Nickel	One-light	11-1/2" dia., 3-3/4" ht.	1 13w GU24 CFL included	T24
P3764-20EBWB	Antique Bronze				
P3765-09EBWB	Brushed Nickel	Two-light	14" dia., 4-3/4" ht.	2 13w GU24 CFL included	T24
P3765-20EBWB	Antique Bronze				



P3760-09EBWB



P3764-09EBWB



P3765-09EBWB



P3760-20EBWB



P3764-20EBWB



P3765-20EBWB

ETCHED RIBBED GLASS GU24

Etched ribbed glass with metal trim. Energy efficient lamps included.

PRODUCT NO.	FINISH	DESCRIPTION	SIZE	LAMP(S)	
P3761-09EBWB	Brushed Nickel	One-light	11-1/2" dia., 4-1/2" ht.	1 13w GU24 CFL included	T24
P3762-09EBWB	Brushed Nickel	Two-light	14" dia., 4-3/4" ht.	2 13w GU24 CFL included	






P3761-09EBWB



P3762-09EBWB

ALABASTER GLASS GU24

Dome shaped glass with metal trim and decorative knobs.
Energy efficient.

PRODUCT NO.	FINISH	DESCRIPTION	SIZE	LAMP(S)	
P3924-09EB	Brushed Nickel	One-light	11-3/8" dia., 5-1/2" ht.	1 GU24 CFL 13w max.	
P3924-20EB	Antique Bronze				
P3925-09EB	Brushed Nickel	Two-light	13-1/4" dia., 5-3/4" ht.	2 GU24 CFL each 18w max.	
P3925-20EB	Antique Bronze				
P3926-09EB	Brushed Nickel	Three-light	15-1/4" dia., 6-5/8" ht.	3 GU24 CFL each 18w max.	
P3926-20EB	Antique Bronze				



P3924-09EB



P3924-20EB



P3925-09EB



P3925-20EB



P3926-09EB



P3926-20EB

WISTEN GU24

Wisten's domed glass offers a simple,
modern and elegant touch.

P3290-09EBWB Brushed Nickel
14" dia., 7" ht.
Two 13w GU24 CFL lamps, included.








P3290-09EBWB

ROUND CLOUDS GU24

White contoured acrylic clouds with smooth finish texture. Twist on installation. Wall or ceiling mount.

White contoured acrylic clouds.

PRODUCT NO.	FINISH	DESCRIPTION	SIZE	LAMP(S)		
P3433-30WB	White	Two-light	11-1/4" dia., 3-5/8" ht.	2 GU24 CFL lamps, each 13w max. included	ADA	
P3637-30WB	White	Three-light	14" dia., 3-1/2" ht.	3 GU24 CFL lamps, each 13w max. included	ADA	
P7384-30WB	White	Four-light	18" dia., 4-1/8" ht.	4 GU24 CFL lamps each 13w max. included		



P7384-30WB








P3433-30WB



P3637-30WB

MAIER GU24

Etched white opal acrylic features a smooth rounded frame. Wall or ceiling mount.

PRODUCT NO.	FINISH	DESCRIPTION	SIZE	LAMP(S)	
P3675-09WB	Brushed Nickel	Three-light	18" dia., 5-1/4" ht.	3 26w GU24 CFL included	
P3675-30WB	White				
P3910-09	Brushed Nickel	One-light	9" dia., 4-3/8" ht.	1 26w GU24 CFL	
P3910-09WB	Brushed Nickel	One-light	9" dia., 4-3/8" ht.	1 26w GU24 CFL included	
P3911-09	Brushed Nickel	Two-light	14" dia., 4-3/4" ht.	2 26w GU24 CFL	
P3911-09WB	Brushed Nickel	Two-light	14" dia., 4-3/4" ht.	2 26w GU24 CFL included	



P3675-30WB



P3910-09
P3910-09WB




P3911-09
P3911-09WB



P3675-09WB

6" FITTER GU24

PRODUCT NO.	FINISH	DESCRIPTION	SIZE	LAMP(S)
P3408-09WB	Brushed Nickel	One-light	7-1/2" dia.,	1 13w GU24 included 
P3408-20WB	Antique Bronze	4-5/8" ht.	4-5/8" ht.	
P3408-30WB	White			



P3408-09WB




P3408-20WB



P3408-30WB

8" FITTER GU24

PRODUCT NO.	FINISH	DESCRIPTION	SIZE	LAMP(S)
P3410-09WB	Brushed Nickel	Two-light	9-1/2" dia.,	2 13w GU24 included 
P3410-20WB	Antique Bronze		5-1/4" ht.	
P3410-30WB	White			



P3410-09WB



P3410-20WB



P3410-30WB

WISTEN GU24

Simple, modern and elegant, the Wisten family features a sculptured linear look. Etched glass for soft contemporary feel.

FINISHES

- Brushed Nickel - 09
- Antique Bronze - 20

ONE-LIGHT

P3360-09 Brushed Nickel
P3360-20 Antique Bronze
 Wall or ceiling mount.
 5-1/4" W., 8-1/2" ht.
 One 18w GU24 CFL lamp.

T24

THREE-LIGHT

P3361-09 Brushed Nickel
P3361-20 Antique Bronze
 Wall or ceiling mount.
 11" W. canopy, 8-1/4" ht.
 Three 18w GU24 CFL lamps.

T24

FOUR-LIGHT

P3362-09 Brushed Nickel
P3362-20 Antique Bronze
 Wall or ceiling mount.
 40" W., 9" ht.
 Four 18w GU24 CFL lamps.

T24

THREE-LIGHT

P3363-09 Brushed Nickel
P3363-20 Antique Bronze
 Wall or ceiling mount.
 26" W., 9" ht.
 Three 18w GU24 CFL lamps.

T24



P3360-09



P3361-09



P3363-09



P3362-09



P3360-20



P3361-20



P3363-20



P3362-20



Shown: P3925-09WB - Close-to-Ceiling & P2501-09 Ceiling Fan With P2621-09FBWB Light Kit (Image: Eastwood Homes)

Ceiling Fans & Light Kits

CEILING FANS ARE ECONOMICAL & MULTI-BENEFICIAL TO CONSUMER

All Progress Lighting ceiling fans comply with the Department of Energy's (DOE) standards and are listed by California Energy Commission per Title 20. When they are used along with a climate controlled system, such as air conditioner or heater, a fan can save you money on your power bill. A ceiling fan will help keep you cooler in the summer and warmer in the winter. Any of the fans shown below can be operated with or without a light kit. Add a T24 compliant light kit to enhance any room's decor and lighting.

P2500-30



OTHER FINISHES

- P2500-09
- P2500-20

P2501-09



OTHER FINISHES

- P2501-20
- P2501-30
- P2501-30W


P2502-20



OTHER FINISHES

- P2502-30
- P2502-80

P2503-30W



OTHER FINISHES

- P2503-09
- P2503-20

P2521-09CH



OTHER FINISHES

- P2521-09
- P2521-09WA
- P2521-20
- P2521-77
- P2521-80
- P2521-81

P2524-09



OTHER FINISHES

- P2524-30

P2525-30



OTHER FINISHES

- P2525-09

P2526-20



P2530-09



OTHER FINISHES

- P2530-20
- P2530-30W

P2531-20



OTHER FINISHES

- P2531-09

P2533-20



LED LIGHT KITS

Universal-style light kits with quick connect wiring.

LED CEILING FAN LIGHT KIT

P2659-09 Brushed Nickel

P2659-20 Antique Bronze

Etched white glass.

11-1/8" dia., 4" ht.

One 3000K 16.5w

LED included.

1265 source lumens,

960 delivered lumens,

90 CRI.



P2659-09



P2659-20

LED CEILING FAN LIGHT KIT

P2660-09 Brushed Nickel

P2660-20 Antique Bronze

Etched alabaster glass.

11-1/4" dia., 5-3/8" ht.

One 3000K 16.3w

LED included.

1241 source lumens,

1150 delivered lumens,

90 CRI.



P2660-09



P2660-20

SCHOOLHOUSE GU24

Schoolhouse opal glass. Universal-style with quick-connect wiring.

P2620-30EBWB White

8-1/4" dia., 7-1/4" ht.

One 13w GU24 CFL

included (non-dimmable).



P2620-30EBWB

GATHER GU24

Universal-style light kit
with quick-connect wiring.

P2658-09WB Brushed Nickel
P2658-20WB Antique Bronze
11" dia., 5-1/2" ht.
Two 13w GU24 CFL included
(non-dimmable).

T24



P2658-09WB



P2658-20WB

ALABASTER BOWL GU24

White alabaster glass. Universal-style light kit
with quick-connect wiring.

P2621-09EBWB Brushed Nickel
P2621-30EBWB White
10-3/4" dia. 6" ht.
Two 13w GU24 CFL
included (non-dimmable).

T24



P2621-09EBWB



P2621-30EBWB

LOW PROFILE GU24

White opal glass. Universal-style light kit with
quick-connect wiring.

P2602-09EBWB Brushed Nickel
P2602-20EBWB Antique Bronze
P2602-30EBWB White
10-5/8" dia., 3-7/8" ht.
Two 13w GU24 CFL
included (non-dimmable).

T24



P2602-09EBWB



P2602-30EBWB



P2602-20EBWB



Shown: P2137-20 with JA8 compliant LED lamp
(Image: Micamy Design Studios)

Bath

TRINITY GU24

Soft angles and curved lines in the Trinity collection are ideal for today's understated interiors. Etched glass shades that curve out can be mounted upward or downward.



P3190-09EBWB

ONE-LIGHT CFL BATH

P3190-09EBWB Brushed Nickel
6-1/2" W., 7-1/2" ht.
Extends 9".
One 13w GU24 CFL lamp,
included.

T24

TWO-LIGHT CFL BATH

P3191-09EBWB Brushed Nickel
17-1/2" W., 8-1/8" ht.
Extends 7-1/2".
Two 13w GU24 CFL lamps,
included.

T24

THREE-LIGHT CFL BATH

P3192-09EBWB Brushed Nickel
24" W., 8-1/8" ht.
Extends 7-1/2".
Three 13w GU24 CFL lamps,
included.

T24

FOUR-LIGHT CFL BATH

P3193-09EBWB Brushed Nickel
33-1/4" W., 8-1/8" ht.
Extends 7-1/2".
Four 13w GU24 CFL lamps,
included.

T24



P3192-09EBWB



P3191-09EBWB



P3193-09EBWB

ALABASTER GLASS GU24

Etched Alabaster Glass with soft curves. Brushed Nickel complements stepped backplates.

PRODUCT NO.	FINISH	DESCRIPTION	SIZE	LAMP(S)	
P3052-09EBWB	Brushed Nickel	Two-light	18" W., 7-1/4" ht. Extends 7-1/4".	2 GU24 CFL lamps, each 13w max, included	T24
P3053-09EBWB	Brushed Nickel	Three-light	24" W., 7-1/4" ht. Extends 7-1/4".	3 GU24 CFL lamps, each 13w max, included	T24
P3054-09EBWB	Brushed Nickel	Four-light	30" W., 7-1/4" ht. Extends 7-1/4".	4 GU24 CFL lamps, each 13w max, included	T24



P3052-09EBWB



P3053-09EBWB



P3054-09EBWB

GATHER GU24

Gather possesses a smart simplicity to complement today's home. Featuring a glamorous Brushed Nickel finished frame, this collection allows you to decorate an entire home with confidence and style.

ONE-LIGHT CFL BATH
P2706-09EBWB Brushed Nickel
5" W., 7-1/2" ht.
Extends 6-1/2". H/CTR 2-5/8".
One 13w GU24 CFL, included.

T24



P2706-09EBWB



P2708-09EBWB

TWO-LIGHT CFL BATH
P2707-09EBWB Brushed Nickel
12" W., 7-1/2" ht.
Extends 6-1/2". H/CTR 2-1/2".
Two 13w GU24 CFL, included.

T24



P2707-09EBWB



P2709-09EBWB

THREE-LIGHT CFL BATH
P2708-09EBWB Brushed Nickel
24" W., 7-1/2" ht.
Extends 6-1/2". H/CTR 2-1/2".
Three 13w GU24 CFL, included.

T24

FOUR-LIGHT CFL BATH
P2709-09EBWB Brushed Nickel
30" W., 7-1/2" ht.
Extends 6-1/2". H/CTR 2-1/2".
Four 13w GU24 CFL, included.

T24



Shown: P3192-09EBWB
(Image: Beazer Homes)




Shown: P5644, 20, 30K, Square Cylinder

Outdoor



OUTDOOR INSTALLATION ONLY

ARRIVE LED



Arrive LED lanterns feature a die-cast aluminum powder coated frame and heavily textured glass to create a unique visual effect.



P6067-3130K9



P6069-3130K9



P6068-3130K9



P6076-3130K9

FINISH

- Black - 31

SMALL WALL LANTERN

P6067-3130K9 Black
6" W., 8-3/4" ht.
Extends 7-3/8". H/CTR 4".
One 9w LED module included.



MEDIUM WALL LANTERN

P6068-3130K9 Black
7-1/2" W., 11-1/8" ht.
Extends 8-3/4". H/CTR 5-1/4".
One 9w LED module included.



LARGE WALL LANTERN

P6069-3130K9 Black
9" W., 13" ht.
Extends 10-1/4". H/CTR 5-3/4".
One 17w LED module included.



EXTRA LARGE WALL LANTERN

P6076-3130K9 Black
11" W., 16" ht.
Extends 12-1/4". H/CTR 8-5/8".
One 17w LED module included.



POST LANTERN

P6427-3130K9 Black
9" sq., 15-7/8" ht.
Fits 3" post (order separately).
One 17w LED module included.



HANGING LANTERN

P6527-3130K9 Black
9" sq., 15-1/8" ht. Overall ht.
w/chain 88-1/4"; wire 15'.
One 17w LED module included.



LED FEATURES

- 120v AC, replaceable module
- 9w: 623 lumens, 69.2 lumens/watt
17w: 1211 lumens, 71.2 lumens/watt
- 3000K color temperature; 90 CRI
- Dimmable to 10% brightness with many ELV type dimmers

PROGRESS **LED**




P6527-3130K9



P6427-3130K9

ENDORSE LED



Endorse celebrates the traditional form of a gas-powered coach light with illumination from a modern LED source. A die-cast aluminum, powder coated frame creates an intriguing visual effect with clear beveled glass. To add a decorative element in the lantern, a fluted frosted glass column is offered as an accessory.

FINISH

- Black - 31

SMALL WALL LANTERN

P6056-3130K9 Black
6-3/4" W., 12" ht.
Extends 7-5/8". H/CTR 3-1/4".
One 9w LED module included.



LED FEATURES

- 120v AC, module
- 623 lumens, 69.2 lumens/watt
- 3000K color temperature; 90 CRI

MEDIUM WALL LANTERN

P6057-3130K9 Black
8-3/4" W., 14-3/4" ht.
Extends 9-3/4". H/CTR 4".
One 9w LED module included.



PROGRESS LED

LARGE WALL LANTERN

P6058-3130K9 Black
10-3/4" W., 17-3/4" ht.
Extends 11-3/4". H/CTR 4".
One 9w LED module included.



HANGING LANTERN

P6526-3130K9 Black
8-3/4" sq., 14-1/2" ht.
Overall ht. w/chain 101"; wire 12'.
One 9w LED module included.



P6526-3130K9



P6056-3130K9



P6056-3130K9

*Shown with P8774-31
accessory column*



P6057-3130K9



P6057-3130K9

*Shown with P8775-31
accessory column*



P6058-3130K9

WISH LED

The Wish Collection recognizes the growing trend seeking to protect views of the night sky. This innovative style conceals a full cutoff shield to combine a traditional lantern aesthetic with dark sky performance. To further extend the versatility of this classic style, the shield can be removed for those that like the style, but don't require dark sky compliance. Available in wall, hanging or post applications. Post light does not include full cutoff shield.

FINISHES

- Antique Bronze - 20
- Black - 31

SMALL WALL LANTERN

P6084-2030K9 Antique Bronze
P6084-3130K9 Black
 7" W., 10-3/8" ht.
 Extends 8-5/8". H/CTR 3-1/8".
 One 9w LED module included.



LED FEATURES

- 120V AC, module
- 9w: 623 lumens, 69.2 lumens/watt
- 17w: 1211 lumens, 71.2 lumens/watt
- 3000K color temperature; 90+ CRI
- TM-21 60,000 hr. life

MEDIUM WALL LANTERN

P6085-2030K9 Antique Bronze
P6085-3130K9 Black
 9" W., 12-1/2" ht.
 Extends 10-1/2". H/CTR 3-1/8".
 One 17w LED module included.



PROGRESS **LED**

POST LANTERN

P6424-2030K9 Antique Bronze
P6424-3130K9 Black
 Dark Sky shield not included.
 9" dia., 15-1/4" ht.
 Fits 3" post (order separately).
 One 9w LED module included.



Dark sky cylinder included, except the post lantern.

HANGING LANTERN

P6524-2030K9 Antique Bronze
P6524-3130K9 Black
 9" sq., 12-1/2" ht.
 Overall ht. w/chain 87-1/2"; wire 15'.
 One 17w LED module included.



P6524-2030K9



P6524-3130K9



P6084-2030K9



P6084-3130K9



P6085-2030K9



P6085-3130K9



P6424-2030K9



P6424-3130K9

DERBY LED



Craftsman styling marries traditional and rustic details. Derby boasts an artistic glass diffuser with a die-cast aluminum, powder coated Antique Bronze frame.

FINISH

- Antique Bronze - 20

SMALL WALL LANTERN

P5749-2030K9 Antique Bronze
6-1/2" W., 8-3/8" ht.
Extends 7-3/8". H/CTR 3".
One 9w LED module included.



LED FEATURES

- 120v AC, module
- 9w: 623 lumens, 69.2 lumens/watt
- 17w: 1211 lumens, 71.2 lumens/watt
- 3000K color temperature; 90 CRI

MEDIUM WALL LANTERN

P5750-2030K9 Antique Bronze
8-1/2" W., 11-1/4" ht.
Extends 9-3/8". H/CTR 4-1/4".
One 9w LED module included.



LARGE WALL LANTERN

P5751-2030K9 Antique Bronze
10-5/8" W., 15-1/2" ht.
Extends 11-5/8". H/CTR 3-3/8".
One 9w LED module included.



FLUSH MOUNT

P6017-2030K9 Antique Bronze
10" sq., 5-1/2" ht.
One 17w LED module included.



P6017-2030K9



P5749-2030K9



P5750-2030K9



P5751-2030K9

BROOKSIDE LED

Get inspired by vintage undertones and train station styling with this outdoor lantern collection. Available in Brushed Nickel, Antique Bronze, aluminium with Gilded Iron finish or solid brass Antique Nickel or solid Copper that ages to a patina finish. Dark Sky compliant.

FINISHES

- Brushed Nickel - 09
- Copper - 14
- Antique Bronze - 20
- Gilded Iron - 71
- Antique Nickel - 81

LED PENDANT

P5024-0930K9 Brushed Nickel

P5024-2030K9 Antique Bronze

12" dia., 9-1/8" ht.

Overall ht. w/stem 65"; wire 15'.

One 17w LED module included.



P5024-0930K9



P5024-2030K9

LARGE WALL LANTERN

P5723-1430K9 Copper

P5723-7130K9 Gilded Iron

P5723-8130K9 Antique Nickel

12" W., 12-1/4" ht.

Extends 13-1/4". H/CTR 6-7/8".

One 17w LED module included.



P5723-1430K9



P5723-7130K9

LED FEATURES

- 120v AC, module
- 1211 lumens, 71.2 lumens/watt
- 3000K color temperature; 90 CRI



P5723-8130K9

PIER 33

Outdoor hanging and wall lanterns from the Pier 33 collection feature coastal undertones and a design reminiscent of industrial spaces. This LED fixture is comprised of a die-cast frame with a clear seeded glass that complements a Black finish.

FINISH

- Black - 031

LED HANGING LANTERN

P550010-031-30 Black
8-1/8" dia., 13-1/4" ht.
Overall ht. 79-1/2". wire 10".
One 9w LED module included.



LED FEATURES

- 120v AC, module
- 9w 624 lumens, 66 lumens/watt
- 3000K color temperature; 90 CRI

PROGRESS LED



P560034-031-30

LED WALL LANTERN

P560034-031-30 Black
8-1/8" dia., 13" ht.
Extends 9". H/CTR 3-1/4".
One 9w LED module included.



ELLIPSIS

An LED wall lantern featuring an etched white pillar candle inside a clear globe glass design. A replaceable AC LED module sits at the base of the Black frame and illuminates upward for a striking visual effect.

FINISH

- Black - 031

LED WALL LANTERN

P560000-031-30 Black
8" W., 15-1/2" ht.
Extends 11-7/8". H/CTR 7-3/4".
One 9w LED module included.



LED FEATURES


- 120v AC, module
- 9w 670 lumens, 71 lumens/watt
- 3000K color temperature; 90 CRI

PROGRESS LED



P560000-031-30

CADENCE GU24



Clear seeded water glass panes with etched pillar diffuser uses energy efficient compact fluorescent lamp.

FINISH

- Black - 31

POST LANTERN

P6439-31 Black
10" dia., 23" ht.
Fits 3" post (order separately).
One GU24 lamp,
26w max.



HANGING LANTERN

P6539-31 Black
10" dia., 24-5/8" ht.
Overall ht. w/chain 100", wire 10".
One GU24 lamp,
26w max.



SMALL WALL LANTERN

P6626-31 Black
6-1/8" W., 18-7/8" ht.
Extends 7-1/2". H/CTR 9-1/4".
One GU24 lamp,
18w max.



MEDIUM WALL LANTERN

P6627-31 Black
8" W., 24-3/4" ht.
Extends 9-1/4". H/CTR 13-3/8".
One GU24 lamp,
26w max.



LARGE WALL LANTERN

P6628-31 Black
10" W., 31" ht.
Extends 11-3/8". H/CTR 14-1/8".
One GU24 lamp,
26w max.



EXTRA-LARGE WALL LANTERN

P6629-31 Black
12" W., 38" ht.
Extends 13-1/4". H/CTR 18-1/4".
One GU24 lamp,
26w max.



P6626-31



P6539-31



P6628-31



P6627-31



P6629-31



P6439-31

DESIGN+SERIES™

CRAWFORD GU24

Transform the outdoors with timeless styling. Die-cast aluminum with clear water glass and etched pillar. For use with compact fluorescent lamp.

FINISH

- Black - 31

POST LANTERN

P6440-31 Black
9-7/8" W., 24-5/8" ht.
Fits 3" post (order separately,).
One GU24 CFL lamp,
26w max.

T24

HANGING LANTERN

P6540-31 Black
9-7/8" dia., 26-5/8" ht.
Overall ht. w/ chain 102"; wire 10'.
One GU24 CFL lamp,
26w max.

T24

SMALL WALL LANTERN

P6630-31 Black
6-1/2" W., 1-1/2" ht.
Extends 8-3/4". H/CTR 8".
One GU24 CFL lamp,
26w max.

T24

MEDIUM WALL LANTERN

P6631-31 Black
8-1/2" W., 20-1/2" ht.
Extends 11".
H/CTR 8-3/8".
One GU24 CFL lamp,
26w max.

T24

LARGE WALL LANTERN

P6632-31 Black
9-7/8" W., 28-7/8" ht.
Extends 12-5/8". H/CTR 8-3/8".
One GU24 CFL lamp,
26w max.

T24

EXTRA-LARGE WALL LANTERN

P6633-31 Black
12" W., 32-7/8" ht.
Extends 14-3/4". H/CTR 14-7/8".
One GU24 CFL lamp,
26w max.

T24



Clear seeded water glass panes with etched pillar diffuser.
GU24 sockets for use with energy efficient lamps.

FINISH

- Black - 31

POST LANTERN

P6438-31 Black
9-1/2" dia., 22-3/8" ht.
Fits 3" post (order separately).
One GU24 lamp,
26w max.

T24

HANGING LANTERN

P6538-31 Black
12-1/2" dia., 25-1/4" ht.
Overall ht. w/chain 100-1/2", wire 10'.
One GU24 lamp,
26w max.

T24

SMALL WALL LANTERN

P6619-31 Black
5-5/8" W., 13-3/8" ht.
Extends 6-3/4". H/CTR 6-3/8".
One GU24 lamp,
18w max.

T24

MEDIUM WALL LANTERN

P6620-31 Black
7-1/2" W., 18-3/8" ht.
Extends 8-3/8". H/CTR 10-1/2".
One GU24 lamp,
26w max.

T24

LARGE WALL LANTERN

P6621-31 Black
9-1/2" W., 26-1/4" ht.
Extends 10-1/4". H/CTR 12-3/4".
One GU24 lamp,
26w max.

T24

EXTRA-LARGE WALL LANTERN

P6622-31 Black
12-1/2" W., 34-3/8" ht.
Extends 13-1/2". H/CTR 18-5/8".
One GU24 lamp,
26w max.

T24



P6538-31



P6619-31



P6620-31



P6621-31



P6438-31



P6622-31



Maison offers French country styling for a variety of home settings. Classic and formal clear water seeded glass in a die-cast aluminum frame. GU24 version with etched pillar diffuser.

FINISH

- Black - 31

POST LANTERN

P6441-31 Black
 10-1/2" dia., 26-3/8" ht.
 Fits 3" post (order separately).
 One GU24 lamp,
 26w max.

T24

LARGE WALL LANTERN

P6636-31 Black
 8-1/2" W., 19-3/4" ht.
 Extends 8-7/8". H/CTR 13-3/8".
 One GU24 lamp,
 26w max.

T24

HANGING LANTERN

P6541-31 Black
 10-1/2" dia., 24-1/2" ht. Overall ht.
 w/chain 100-1/2", wire 10".
 One GU24 lamp,
 26w max.

T24

EXTRA-LARGE WALL LANTERN

P6637-31 Black
 10-1/2" W., 23-3/4" ht.
 Extends 11-1/4". H/CTR 16-3/8".
 One GU24 lamp,
 26w max.

T24

SMALL WALL LANTERN

P6634-31 Black
 5-3/4" W., 13-5/8" ht.
 Extends 6-1/8". H/CTR 9-1/8".
 One GU24 lamp,
 18w max.

T24

MEDIUM WALL LANTERN

P6635-31 Black
 7-1/4" W., 16-7/8" ht.
 Extends 7-7/8". H/CTR 11-3/4".
 One GU24 lamp,
 26w max.

T24



P6634-31



P6541-31



P6636-31



P6635-31



P6637-31



P6441-31

PEDIGREE GU24



Durable powder coat finish. Cast pyramidal block and fluted uprights. Energy efficient outdoor lanterns with etched seeded glass. Cast aluminum construction in an Autumn Haze finish.

FINISH

- Autumn Haze - 97

SMALL WALL LANTERN

P5980-97 Autumn Haze
7" W., 10" ht.
Extends 8-1/2". H/CTR 2-5/8".
One GU24 base CFL lamp,
26w max.



HANGING LANTERN

P6503-97 Autumn Haze
9" dia., 13-5/8" ht.
Overall ht w/chain 88"; wire 15'.
One GU24 base CFL lamp,
26w max.



MEDIUM WALL LANTERN

P5981-97 Autumn Haze
9" W., 13-3/8" ht.
Extends 10-1/2". H/CTR 5-3/4".
One GU24 base CFL lamp,
26w max.



EXTRA LARGE WALL LANTERN

P6607-97 Autumn Haze
13-1/2" W., 19-3/8" ht.
Extends 15-3/4". H/CTR 6-3/4".
One GU24 base CFL lamp,
42w max.



LARGE WALL LANTERN

P5982-97 Autumn Haze
11-1/2" W., 16-1/2" ht.
Extends 13-1/2". H/CTR 5-3/4".
One GU24 base lamp,
26w max.



POST LANTERN

P6403-97 Autumn Haze
9" dia., 16-3/8" ht.
Fits 3" post (order separately).
One GU24 base CFL lamp,
26w max.



P5980-97



P6503-97



P5982-97



P5981-97



P6607-97



P6403-97

ASHMORE GU24

Handsome details, quill-scrolled arms and decorative finials. Textured Black or Antique Bronze finish. Die-cast aluminum construction with etched water glass.

MEDIUM WALL LANTERN

P5875-20WB Antique Bronze

P5875-31WB Textured Black

Etched glass.

8-3/8" W., 16-5/8" ht.

Extends 10-1/2". H/CTR 4-1/2".

One GU24 CFL lamp,

26w max. included.

T24



P5875-20WB



P5875-31WB

CRAWFORD GU24

Transform the outdoors with timeless styling. Die-cast aluminum with etched flat glass panels. For use with compact fluorescent lamp.

MEDIUM WALL LANTERN

P5686-31 Black

P5686-108 Oil Rubbed Bronze

8-1/2" W., 16-3/4" ht.

Extends 11-1/8" H/CTR 9-5/8".

One GU24 CFL lamp,

26w max.

T24



P5686-108



P5686-31

WESTPORT LED

SMALL WALL LANTERN

P5861-3130K9 Black

Meets CA Title 24 Standards (JA8)

6-7/8" W., 10-1/4" ht.

Extends 8-3/8". H/CTR 3-1/8".

One 9w LED module included.

670 lumens per module.



P5861-3130K9

WESTPORT LED

Westport LED offers traditional styling to complement a variety of home décor options. A durable, die-cast aluminum frame cradles a softly diffused, seeded glass shade.

FINISHES

- Antique Bronze - 20
- Black - 31

FLUSH MOUNT

P3883-2030K9 Antique Bronze
P3883-3130K9 Black
 9" dia., 7-1/4" ht.
 One 17w LED module included.



POST LANTERN

P5445-2030K9 Antique Bronze
P5445-3130K9 Black
 9" dia., 16-3/8" ht.
 Fits 3" post (order separately).
 One 9w LED module included.



SMALL WALL LANTERN

P5862-2030K9 Antique Bronze
P5862-3130K9 Black
 6-7/8" W., 10-1/4" ht.
 Extends 8-3/8". H/CTR 3-1/8".
 One 9w LED module included.



MEDIUM WALL LANTERN

P5863-2030K9 Antique Bronze
P5863-3130K9 Black
 9" W., 12-7/8" ht.
 Extends 10-3/8". H/CTR 3-3/4".
 One 9w LED module included.



LARGE WALL LANTERN

P5864-2030K9 Antique Bronze
P5864-3130K9 Black
 11" W., 15-3/8" ht.
 Extends 12-7/8". H/CTR 4".
 One 17w LED module included.



LED FEATURES

- 120v AC, module
- 9w: 623 lumens, 69.2 lumens/watt
- 17w: 1211 lumens, 71.2 lumens/watt
- 3000K color temperature; 90 CRI



P3883-2030K9



P3883-3130K9



P5862-2030K9



P5862-3130K9



P5863-2030K9



P5863-3130K9



P5445-2030K9



P5445-3130K9



P5864-2030K9



P5864-3130K9

EAST HAVEN LED

East Haven offers contemporary styling to complement today's home styles. A Black or Antique Bronze frame cradles a seeded glass shade.

FINISHES

- Antique Bronze - 20
- Black - 31

SMALL WALL LANTERN

P6077-2030K9 Antique Bronze
P6077-3130K9 Black
 5-3/4" W., 7-7/8" ht.
 Extends 7-1/2". H/CTR 4-3/4".
 One 9w LED module included.



MEDIUM WALL LANTERN

P6078-2030K9 Antique Bronze
P6078-3130K9 Black
 7-1/2" W., 9-3/4" ht.
 Extends 9-1/8". H/CTR 4-3/4".
 One 9w LED module included.



LARGE WALL LANTERN

P6079-2030K9 Antique Bronze
P6079-3130K9 Black
 9-1/2" W., 12" ht.
 Extends 11-1/8". H/CTR 4-3/4".
 One 17w LED module included.



POST LANTERN

P6430-2030K9 Antique Bronze
P6430-3130K9 Black
 7-1/2" dia., 15" ht.
 Fits 3" post (order separately).
 One 9w LED module included.



HANGING LANTERN

P6530-2030K9 Antique Bronze
P6530-3130K9 Black
 7-1/2" dia., 10-3/8" ht.
 Overall ht. w/chain 86-1/2";
 wire 15'.
 One 9w LED
 module included.



LED FEATURES

- 120V AC LED module
- 9w: 623 lumens, 69.2 lumens/watt
- 17w: 1211 lumens, 71.2 lumens/watt
- 3000K color temperature; 90+ CRI
- TM-21 60,000 hr. life

PROGRESS **LED**



P6530-2030K9



P6530-3130K9



P6077-2030K9



P6077-3130K9



P6078-2030K9



P6078-3130K9



P6430-2030K9



P6430-3130K9



P6079-2030K9



P6079-3130K9

WESTPORT GU24



Add a touch of rustic appeal with beaded detailing. Etched seeded glass with die-cast aluminum frames with durable powder coat finish.

FINISHES

- Antique Bronze - 20
- Black - 31

FLUSH MOUNT

P3883-20WB Antique Bronze

P3883-31WB Black

9" dia., 10-1/2" ht.

One 13w GU24 CFL lamp, (included).

T24

SMALL WALL LANTERN

P5862-20WB Antique Bronze

P5862-31WB Black

6-7/8" W., 12-3/4" ht.

Extends 8-3/8". H/CTR 3-1/4".

One 13w GU24 CFL lamp, (included).

T24

MEDIUM WALL LANTERN

P5863-20WB Antique Bronze

P5863-31WB Black

9" W., 16" ht.

Extends 10-3/8". H/CTR 3-1/2".

One 13w GU24 CFL lamp, (included).

T24

LARGE WALL LANTERN

P5864-20WB Antique Bronze

P5864-31WB Black

11" W., 19-1/2" ht.

Extends 12-7/8". H/CTR 4-5/8".

One 18w GU24 CFL lamp, (included)

T24



P3883-20WB



P3883-31WB



P5862-20WB



P5862-31WB



P5863-20WB



P5863-31WB



P5864-20WB



P5864-31WB

ROMAN COACH GU24

A timeless style with environmentally friendly benefits. Etched seeded glass in Brushed Nickel, Antique Bronze or Black finishes. Solid brass and aluminum construction.

FINISHES

- Brushed Nickel - 09
- Antique Bronze - 20
- Black - 31

PRODUCT NO.	FINISH	DESCRIPTION	SIZE	LAMP(S)
P5766-09	Brushed Nickel	One-light wall lantern	6" W., 9-7/8" ht. Extends 7". H/CTR 3-1/2".	1 13w GU24 CFL lamp 26w max. T24
P5766-20	Antique Bronze			
P5770-09	Brushed Nickel	One-light wall lantern	7" W., 15-3/8" ht. Extends 7-1/4". H/CTR 6-7/8".	1 26w GU24 CFL lamp 26w max. T24
P5770-20	Antique Bronze			
P5772-09	Brushed Nickel	One-light wall lantern*	7" W., 26-3/8" ht. w/tail. 19-1/4" ht. w/o tail. Extends 6-7/8". H/CTR 16-1/4".	1 26w GU24 CFL lamp 26w max. T24
P5772-20	Antique Bronze			

*Can be installed with or without tail.



P5766-09



P5766-20



P5770-09



P5770-20



P5772-09
shown without tail



P5772-09
shown with tail



P5772-20
shown with tail

PRODUCT NO.	FINISH	DESCRIPTION	SIZE	LAMP(S)
P5985-09WB	Brushed Nickel	One-light wall lantern	4-5/8" W., 10" ht. Extends 6-1/8". H/CTR 2-3/4".	1 26w GU24 CFL lamp (included) T24
P5985-20WB	Antique Bronze			
P5985-31WB	Black			
P5986-09	Brushed Nickel	One-light wall lantern	4-5/8" W., 8-1/2" ht. Extends 6-1/8". H/CTR 2-3/4".	1 13w GU24 CFL lamp T24
P5986-20	Antique Bronze			
P5986-31	Black			



P5986-09



P5986-20



P5985-09WB



P5985-20WB



P5985-31WB

VALERA GU24

Transform outdoor settings with a bold, straightforward style. Double linear details finished in Brushed Nickel or Antique Bronze over a white acrylic diffuser. Die-cast aluminum construction.

FINISHES

- Brushed Nickel - 09
- Antique Bronze - 20

SMALL WALL LANTERN

P5800-09 Brushed Nickel

P5800-20 Antique Bronze

5-5/8" W., 8" ht.
Extends 4". H/CTR 4".
One GU24 CFL lamp,
18w max.
ADA

T24

MEDIUM WALL LANTERN

P5801-09 Brushed Nickel

P5801-20 Antique Bronze

8-5/8" W., 11" ht.
Extends 4". H/CTR 5-1/2".
One GU24 CFL lamp,
26w max.
ADA

T24

LARGE WALL LANTERN

P5806-09 Brushed Nickel

P5806-20 Antique Bronze

5-5/8" W., 16" ht.
Extends 4". H/CTR 8".
Two GU24 CFL lamps,
each 18w max.
ADA

T24



P5800-09



P5800-20



P5801-09



P5801-20



P5806-09



P5806-20

VALERA LED

FINISHES

- Brushed Nickel - 09
- Architectural Bronze - 129

LED WALL LANTERN

P5800-0930K9 Brushed Nickel
P5800-12930K9 Architectural Bronze
 5-5/8" W., 8" ht.
 Extends 4". H/CTR 4".
 One 9w LED module included.
 623 lumens per module, 90 CRI.
 ADA



P5800-0930K9



P5800-12930K9

LED WALL LANTERN

P5801-0930K9 Brushed Nickel
P5801-12930K9 Architectural Bronze
 8-5/8" W., 11" ht.
 Extends 4". H/CTR 5-1/2".
 One 17w LED module included.
 1211 lumens per module, 90 CRI.
 ADA



P5801-0930K9



P5801-12930K9

LED WALL LANTERN

P5806-0930K9 Brushed Nickel
P5806-12930K9 Architectural Bronze
 5-5/8" W., 16" ht.
 Extends 4". H/CTR 8".
 Two 9w LED modules included.
 623 lumens per module, 90 CRI.
 ADA



P5806-0930K9



P5806-12930K9

LED FEATURES

- 120V AC, module
- 9w: 623 lumens, 69.2 lumens/watt
17w: 1211 lumens, 71.2 lumens/watt
- 3000K color temperature; 90+ CRI
- TM-21 60,000 hr. life

PROGRESS **LED**

BELL LED

Featuring nautical undertones, the Bell outdoor collection offers cage lights reminiscent of industrial architecture. Ideal for use in exterior settings, this LED fixture is available in convertible ceiling/pendant and wall mount options.

FINISHES

- Antique Bronze - 20
- Textured Graphite -136

SMALL WALL LANTERN

P5676-2030K9 Antique Bronze
P5676-13630K9 Textured Graphite
5-1/2" W., 10-5/8" ht.
Extends 7-3/8". H/CTR 3".
One 9w LED module included.



CEILING/PENDANT

P6536-2030K9 Antique Bronze
P6536-13630K9 Textured Graphite
6-5/8" dia., 11-3/8" ht.
Overall ht. w/chain 77"; wire 12'.
One 9w LED module included.



LED FEATURES

- 120V AC LED module
- 623 lumens, 69.2 lumens/watt
- 3000K color temperature; 90+ CRI
- TM-21 60,000 hr. life



P6536-2030K9
Shown as ceiling mount



P6536-13630K9
Shown as ceiling mount



P5676-2030K9



P5676-13630K9

DISTRICT LED

The outdoor lanterns from the District Collection features a metal shade that offers an industrial-inspired design. The versatile vintage form can be used in outdoor applications.

FINISHES

- Antique Bronze - 20
- Metallic Gray -82

LARGE HANGING LANTERN

P5551-2030K9 Antique Bronze

P5551-8230K9 Metallic Gray

12" dia., 8-1/4" ht.

Overall ht. w/cord 130"; wire 12'.

One 9w LED module included.



MEDIUM HANGING LANTERN

P5535-2030K9 Antique Bronze

P5535-8230K9 Metallic Gray

8" dia., 6-1/4" ht.

Overall ht. w/cord 130"; wire 12'.

One 9w LED module included.



MEDIUM WALL LANTERN

P5622-2030K9 Antique Bronze

P5622-8230K9 Metallic Gray

8" W., 8-1/4" ht.

Extends 10-1/4". H/CTR 4-1/8".

One 9w LED module included.



P5622-2030K9

P5622-8230K9

LARGE WALL LANTERN

P5623-2030K9 Antique Bronze

P5623-8230K9 Metallic Gray

12" W., 10-1/2" ht.

Extends 13-1/4". H/CTR 5".

One 9w LED module included.



P5623-2030K9

P5623-8230K9

LED FEATURES

- 120V AC LED module
- 623 lumens, 69.2 lumens/watt
- 3000K color temperature; 90+ CRI
- TM-21 60,000 hr. life

PROGRESS **LED**

Z-1010 LED

A modern outdoor sconce with an open linear frame and seeded glass diffuser. Finished in Black, Satin White and Architectural Bronze.

FINISHES

- Satin White - 028
- Black - 031
- Architectural Bronze - 129

LED WALL LANTERN

P560029-028-30 Satin White

P560029-031-30 Black

P560029-129-30 Architectural Bronze

7-1/2" W., 16" ht.


Extends 4". H/CTR 4-1/4".

One 9w LED module included.

624 source lumens, 66 lumens/watt.



PROGRESS LED



P560029-028-30



P560029-031-30



P560029-129-30

Z-1020 LED

A modern outdoor sconce with white glass shade is suspended in a curved frame that serves as a reflector when illuminated. Finished in Black or Architectural Bronze.

FINISHES

- Black - 031
- Architectural Bronze - 129

LED WALL LANTERN

P560030-031-30 Black

P560030-129-30 Architectural Bronze

7-1/2" W., 13-1/2" ht.

Extends 4-3/4". H/CTR 11-1/8".

One 9w LED module included.

670 source lumens, 71 lumens/watt.



LED FEATURES

- 120v AC, module
- 3000K color temperature; 90 CRI

PROGRESS LED



P560030-031-30



P560030-129-30

ALUMINUM LED CYLINDERS

Sleek, cylindrical forms in elegant finish selections. Die-cast aluminum wall brackets and heavy-duty aluminum framing. Fade and chip-resistant. UL listed for wet locations when used with lens cover.

FINISHES







- Bronze - 20
- White - 30
- Black - 31
- Metallic Gray - 82

LED CYLINDER FEATURES

- 120v AC
- 800 lumens (17w)
1400 lumens (29w)
- 3000K color temperature
- Dimmable to 10% brightness with ELV type dimmers

5" ALUMINUM CYLINDERS

PROGRESS 

PRODUCT NO.	FINISH	DESCRIPTION	SIZE	LAMP(S)	
P5674-20/30K	Bronze	One-light down*	5" W., 7-1/4" ht. Extends 8". H/CTR 2-1/2".	1 17w LED module included	 
P5674-30/30K	White				
P5674-31/30K	Black				
P5674-82/30K	Metallic Gray				
P5675-20/30K	Bronze	Two-light up/down For wet locations specify P8799 top cover lens.	5" W., 14" ht. Extends 8". H/CTR 7".	2 17w LED modules included	 
P5675-30/30K	White				
P5675-31/30K	Black				
P5675-82/30K	Metallic Gray				
P5774-20/30K	Bronze	One-light. Mounts flush to ceiling*	5" dia., 6-1/2" ht.	1 17w LED module included	 
P5774-30/30K	White				
P5774-31/30K	Black				
P5774-82/30K	Metallic Gray				

*Dark sky.



P5774-20/30K



P5774-30/30K



P5774-31/30K



P5774-82/30K



P5674-20/30K



P5674-30/30K



P5674-31/30K



P5674-82/30K



P5675-20/30K



P5675-30/30K









P5675-31/30K



P5675-82/30K

6" ALUMINUM CYLINDERS

PRODUCT NO.	FINISH	DESCRIPTION	SIZE	LAMP(S)	
P5641-20/30K	Bronze	One-light down*	6" W., 12" ht. Extends 8-7/8". H/CTR 4-1/2".	1 29w LED module included	 
P5641-30/30K	White				
P5641-31/30K	Black				
P5641-82/30K	Metallic Gray				
P5642-20/30K	Bronze	Two-light up/down. For wet location specify P8798 top cover lens.	6" W., 18" ht. Extends 8-7/8". H/CTR 8".	2 29w LED modules included	 
P5642-30/30K	White				
P5642-31/30K	Black				
P5642-82/30K	Metallic Gray				
P5741-20/30K	Bronze	One-light cylinder. Mounts flush to ceiling or hangs with pendant accessory kit, page 301.	6" dia., 12" ht.	1 29w LED module included	 
P5741-30/30K	White				
P5741-31/30K	Black				
P5741-82/30K	Metallic Gray				

*Dark sky.



P5741-20/30K



P5741-30/30K



P5741-31/30K



P5741-82/30K



P5641-20/30K



P5641-30/30K



P5641-31/30K



P5641-82/30K



P5642-20/30K



P5642-30/30K



P5642-31/30K



P5642-82/30K

ALUMINUM LED SQUARES

Heavy-duty aluminum construction, die-cast aluminum wall bracket. UL listed for wet locations. Powder coat for chipping and fading resistance. Dark Sky compliant for down light only. 3000K, 90+ CRI.

FINISHES

- Bronze - 20
- White - 30
- Black - 31
- Metallic Gray - 82

LED CYLINDER FEATURES

- 1400 lumens (29w)

PROGRESS **LED**

PRODUCT NO.	FINISH	DESCRIPTION	SIZE	LAMP(S)
P5643-20-30K	Bronze	One-light 6" square LED	6" W., 12" ht. Extends 8-7/8". H/CTR 4-1/2".	1 29w LED module included
P5643-30-30K	White			
P5643-31-30K	Black			
P5643-82-30K	Metallic Gray			
P5644-20-30K	Bronze	Two-light 6" LED up/down square*	6" W., 18" ht. Extends 8-7/8". H/CTR 8".	2 29w LED modules included
P5644-30-30K	White			
P5644-31-30K	Black			
P5644-82-30K	Metallic Gray			



*For use in wet locations, specify P8797-31 top cover.



P5643-20-30K



P5643-30-30K



P5643-31-30K



P5643-82-30K



P5644-20-30K



P5644-30-30K



P5644-31-30K



P5644-82-30K



Shown: P5644-20-30K, Aluminum Squares

CORNICE LED

Modern geometric outdoor LED sconces are designed to complement a range of residential and commercial architectural styles. ADA compliant. Available in Black, Antique Bronze and Metallic Gray finishes.

FINISHES

- Antique Bronze - 20
- Black - 31
- Metallic Gray - 82

LED OUTDOOR WALL SCONCE

P5634-2030K9 Antique Bronze

P5634-3130K9 Black

P5634-8230K9 Metallic Gray

5-1/4" W., 4-3/4" ht.

Extends 4". H/CTR 2-3/8".

One 9w LED module included.

623 Lumens per module

ADA



P5634-2030K9



P5635-2030K9

LED OUTDOOR WALL SCONCE

P5635-2030K9 Antique Bronze

P5635-3130K9 Black

P5635-8230K9 Metallic Gray

6-1/8" W., 5" ht.

Extends 4". H/CTR 2-3/8".

One 9w LED module included.

623 Lumens per module

ADA



P5634-3130K9



P5635-3130K9

PROGRESS **LED**



P5634-8230K9



P5635-8230K9

ANSON GU24

Enjoy a sleek and modern design. White geometric enclosed diffuser framed in Bronze or Brushed Nickel shield. For Indoor or outdoor use.

WALL LANTERN

P5736-09 Brushed Nickel
P5736-129 Architectural Bronze
Can be used indoors or outdoors.
9-1/8" W., 10-1/4" ht.
Extends 3-3/4". H/CTR 5-5/8".
One GU24 CFL lamp, 18w max.
ADA

FINISHES

- Brushed Nickel - 09
- Architectural Bronze - 129



P5736-09



P5736-129



ANSON LED

One-light ADA wall lantern with polycarbonate diffuser and stainless steel frame. 3000 K, 90+CRI, 1452 lumens.

FINISHES

- Stainless Steel - 135
- Architectural Bronze - 129

WALL LANTERN

P560001-135-30 Stainless Steel
P560001-129-30 Architectural Bronze
10" W., 3" ht.
One 3000K 17w LED
module included.
ADA



P560001-135-30



P560001-129-30



LED BULKHEADS

Robust and energy efficient, LED bulkheads are a general-purpose luminaire. Comprised of a die-cast aluminum frame and polycarbonate diffuser. Fixtures are impact resistant and offer various mounting options and can be widely adopted for outdoor applications.

FINISHES

○ White - 30

● Black - 31

PRODUCT NO.	FINISH	DESCRIPTION	MOUNTING	SIZE	LAMP(S)
P3647-3030K9	White	Oval	Wall or ceiling	6-1/2" W., 10-1/2" ht.	1 9w LED, module included.
P3647-3130K9	Black	Oval	Wall or ceiling	6-1/2" W., 10-1/2" ht.	1 9w LED, module included.
P3648-3030K9	White	Round	Wall or ceiling	9-1/2" dia., 4-3/8" ht.	1 17w LED module included.
P3648-3130K9	Black	Round	Wall or ceiling	9-1/2" dia., 4-3/8" ht.	1 17w LED module included.
P3649-3030K9	White	Oval	Wall or ceiling	6-1/2" W., 10-1/2" ht.	1 9w LED, module included.
P3649-3130K9	Black	Oval	Wall or ceiling	6-1/2" W., 10-1/2" ht.	1 9w LED, module included.
P3650-3030K9	White	Round	Wall or ceiling	9-1/2" dia., 4-1/2" ht.	1 17w LED, module included.
P3650-3130K9	Black	Round	Wall or ceiling	9-1/2" dia., 4-1/2" ht.	1 17w LED, module included.

LED FEATURES

- 120V AC Replaceable LED module
- 17w: 1211 lumens , 71.2 lumens/watt
- 9w: 623 lumens, 69.2 lumens/watt
- 3000K color temperature; 90+ CRI
- TM-21 60,000 hr. life
- Dimmable to 10% with many ELV type dimmers

PROGRESS **LED**



P3647-3030K9
shown wall-mounted



P3647-3130K9
shown ceiling-mounted



P3648-3130K9
shown wall-mounted



P3648-3030K9
shown ceiling-mounted



P3649-3130K9
shown wall-mounted



P3649-3030K9
shown ceiling-mounted



P3650-3130K9
shown wall-mounted



P3650-3030K9
shown ceiling-mounted

MILFORD LED

Etched glass surrounded by a die-cast aluminum frame, ideal for outdoor applications.

FINISHES

- Antique Bronze - 20
- Black - 31



PRODUCT NO.	FINISH	DESCRIPTION	SIZE	LAMP(S)	LUMENS
P3665-2030K9 P3665-3130K9	Antique Bronze Black	One-light flush mount	8-5/8" dia., 4-1/8" ht.	1 17w LED module included	1211 per module
P3673-2030K9 P3673-3130K9	Antique Bronze Black	One-light flush mount	10-5/8" dia., 4-7/8" ht.	1 17w LED module included	1211 per module



P3665-2030K9



P3665-3130K9



P3673-2030K9



P3673-3130K9

PARKER GU24

White acrylic diffuser. Can be used indoors and outdoors. Remove top and bottom end caps for indoor use. Die-cast aluminum construction with powder coat finish.

LARGE WALL LANTERN

P5915-16 Satin Aluminum

P5915-20 Antique Bronze

White acrylic diffuser.

5-3/8" W., 16-7/8" ht.

Extends 4".

Two GU24 CFL lamps,

each 26w max.

ADA




P5915-16



P5915-20

MILFORD CFL

Durable aluminum construction with powder coat finish and white matte acrylic diffuser.

PRODUCT NO.	FINISH	SIZE	LAMP
P5821-20	Antique Bronze	5-3/4" W., 8-3/4" ht.	1 13w GU24 CFL
P5821-31	Black	Extends 4-5/8". H/CTR 5-1/8"	

FINISHES

- Antique Bronze - 20
- Black - 31



P5821-20



P5821-31

NON-METALLIC GU24

Classic White or Black outdoor lanterns.

FINISHES

- White - 30
- Black - 31

PRODUCT NO.	FINISH	DESCRIPTION	SIZE	LAMP(S)
P5816-30WB	White	Polycarbonate wall lantern	6" W., 7-3/4" ht.	1 18w CFL GU24 base (included)
P5816-31WB	Black		Extends 6-1/2".	
P5843-30WB	White	Wall lantern	8-1/4" W., 17-5/8" ht.	1 18w CFL GU24 base (included)
P5843-31WB	Black		Extends 8-1/2". H/CTR 9-3/4".	
P5881-30WB	White	Wall lantern w/white acrylic	6" W., 8-7/8" ht.	1 18w CFL GU24 base (included)
P5881-31WB	Black		Extends 6-7/8". H/CTR 4-1/8".	



P5843-30WB



P5843-31WB



P5816-30WB



P5816-31WB



P5881-30WB



P5881-31WB

LAMPS



MLS13GUWW
13w self-ballasted CFL.
GU24 base.

T24

MLS18GUWW
18w self-ballasted CFL.
GU24 base.

T24

MLS26GUWW
26w self-ballasted CFL.
GU24 base.

T24



E10A19DLED927/JA8
10w, 800 Lumens, 2700K CCT, 90+CRI
E26 medium base. JA8-2016-E

JA8

PHOTO CONTROL

Remote mount photo control installs into standard, rain-tight junction box and includes faceplate and gasket. Max load 2000 watts. Operating range -40 + 140F. Consumes less than 1 watt.

PTORK3010
3" W., 5" ht.



PTORK3010



Shown: P7082-09 Sconce

Sconces

ANSON LED

ADA wall sconce with a polycarbonate diffuser trimmed in Architectural Bronze or Stainless Steel.

P560001-129-30 Architectural Bronze

P560001-135-30 Stainless Steel

10" W., 3" ht.

One 17w LED module included.

1211 source lumens, 90+ CRI.


ADA



PROGRESS **LED**



P560001-129-30



P560001-135-30

ETCHED OPAL GLASS GU24

Enclosed one-piece glass.

P7188-30WB White

13" W., 5-1/4" ht.

Extends 6-1/2". H/CTR 2-1/2".

One GU24 CFL lamp,

13w max., included.

ADA

T24



P7188-30WB

INSPIRE GU24

Off-white linen drum shade.

P7026-30 White

6" W., 9" ht.,

Extends 3-7/8". H/CTR 4-1/2".

One GU24 CFL lamp, 13w max.

ADA

T24



P7026-30

PARKER GU24

Versatile wall sconce can be used indoors and outdoors. Top and bottom cap can be removed for indoor use. Vertical mount only.

P5914-16 Satin Aluminum

P5914-20 Antique Bronze

One-light CFL wall sconce. White acrylic diffuser.

5-3/8" W., 10-1/4" ht. Extends 4".

One GU24 CFL lamp, 26w max.

ADA

T24



P5914-20



P5914-16

OPAL GLASS GU24

Satin opal glass.

FINISHES

- Brushed Nickel - 09
- Antique Bronze - 20

P7052-09EB Brushed Nickel

P7052-20EB Antique Bronze

7" W., 14" ht.

Extends 4". H/CTR 7".

One GU24 base CFL lamp, 26w max.

ADA



P7081-20



P7081-09

P7081-09 Brushed Nickel

P7081-20 Antique Bronze

4-1/2" W., 13-1/2" ht. Extends 4".

H/CTR 9-1/2".

One GU24 base CFL lamp, 26w max.

ADA



P7082-20



P7082-09

P7082-09 Brushed Nickel

P7082-20 Antique Bronze

5" W., 18" ht. Extends 4".

H/CTR 15-3/8".

One GU24 base CFL lamp, 26w max.

ADA



P7052-20EB



P7052-09EB



Showroom: P5113-09EBWB, Pendant &
P4441-09EBWB, Chandelier
(Image: HHunt Homes)

Chandeliers & Pendants

WISTEN GU24

The Wisten Collection features sweeping arcs framing elegant, tapered glass shades. Cool and modern with a casual flair, Wisten provides a signature universal look to any room.

CFL MINI-PENDANT

P5108-09EBWB Brushed Nickel
4" dia., 6-3/4" ht.
Overall ht. w/stem 64"; wire 10'.
One 13w GU24 CFL lamp, included.

T24



GATHER GU24

Simplified frame with updated styling and elegant etched glass shades. Energy efficient fixtures available in the Brushed Nickel finish.

THREE-LIGHT CFL CHANDELIER

P4440-09EBWB Brushed Nickel
18-1/2" dia., 15" ht.
Overall ht. w/chain 60"; wire 8'.
Three 13w GU24
CFL lamps, included.

T24



FIVE-LIGHT CFL CHANDELIER

P4441-09EBWB Brushed Nickel
20-1/2" dia., 15" ht.
Overall ht. w/chain 60"; wire 8'.
Five 13w GU24
CFL lamps, included.

T24



CFL MINI-PENDANT

P5113-09EBWB Brushed Nickel
4" dia., 5-3/4" ht. Overall ht.
w/chain or stem 63"; wire 8'.
One 13w GU24
CFL lamp, included.

T24



TWO-LIGHT INVERTED CFL PENDANT

P3914-09EBWB Brushed Nickel
15" dia., 20-5/8" ht.
Overall ht. w/chain 66"; wire 8'.
Two 13w GU24
CFL lamps, included.

T24





Shown: Recessed Lighting

Index

RECESSED & SURFACE MOUNT

P831-LED p.6



P8080-28-30K p.6



OTHER FINISHES

P8080-09-30K
P8080-20-30K
P8080-31-30K

P8046-20-30K p.6



OTHER FINISHES

P8046-09-30K
P8046-28-30K
P8046-31-30K

P84-LED p.7



P8061-31-30K p.7



OTHER FINISHES

P8061-09-30K
P8061-20-30K
P8061-28-30K

P8176-09-30K p.7



OTHER FINISHES

P8176-20-30K
P8176-28-30K
P8176-31-30K

P87-LED p.8



P8076-20-30K p.8



OTHER FINISHES

P8076-09-30K
P8076-31-30K
P8076-28-30K

P8071-31-30K p.8



OTHER FINISHES

P8071-20-30K
P8071-28-30K
P8071-09-30K

P8240-28-30K p.9



OTHER FINISHES

P8240-82-30K
P8240-20-30K
P8240-31-30K

P8241-20-30K p.9



OTHER FINISHES

P8241-82-30K
P8241-28-30K
P8241-31-30K

P8247-09-30K p.9



OTHER FINISHES

P8247-20-30K
P8247-28-30K
P8247-31-30K

P8108-28-30K p.10



OTHER FINISHES

P8108-20-30K
P8108-31-30K
P8108-82-30K

P8022-82-30K p.10



OTHER FINISHES

P8022-28-30K
P8022-20-30K
P8022-31-30K

P8222-28-30K p.10



P8147-20-30K p.02



OTHER FINISHES

P8147-09-30K
P8147-28-30K
P8147-31-30K

CLOSE-TO-CEILING

P350017-009-30 p.12



OTHER FINISHES

P350017-020-30

P350018-009-30 p.12



OTHER FINISHES

P350018-020-30

P350019-009-30 p.12



OTHER FINISHES

P350019-020-30

P350020-009-30 p.12



OTHER FINISHES

P350020-020-30

P350051-020-30 p.12



OTHER FINISHES

P350051-009-30

P350052-020-30 p.12



OTHER FINISHES

P350052-009-30

P350053-020-30 p.12



OTHER FINISHES

P350053-009-30

P350054-020-30 p.12



OTHER FINISHES

P350054-009-30

P3683-0930K9 p.13



OTHER FINISHES

P3683-2030K9

P3696-0930K9 p.13



OTHER FINISHES

P3696-2030K9

P3939-09 p.13



OTHER FINISHES

P3939-20

P3702-09WB p.13



OTHER FINISHES

P3703-20WB
P3703-30WB

P3703-09WB p.13



OTHER FINISHES

P3703-20WB
P3703-30WB

P3704-09WB p.13



OTHER FINISHES

P3704-20WB
P3704-30WB

P3760-20EBWB p.14



OTHER FINISHES

P3760-09EBWB

P3764-20EBWB p.14



OTHER FINISHES

P3764-09EBWB

P3765-20EBWB p.14



OTHER FINISHES

P3765-09EBWB

P3761-09EBWB p.14



OTHER FINISHES

P3761-20EBWB
P3761-30EBWB

P3762-09EBWB p.14



OTHER FINISHES

P3762-20EBWB
P3762-30EBWB

P3924-20EB p.15



OTHER FINISHES

P3924-09EB

P3925-20EB p.15



OTHER FINISHES

P3925-09EB

P3926-20EB p.15



OTHER FINISHES

P3926-09EB

P3290-09EBWB p.15



OTHER FINISHES

P3290-20EBWB
P3290-30EBWB

P3433-30WB p.16



OTHER FINISHES

P3433-09WB
P3433-20WB

P3637-30WB p.16



OTHER FINISHES

P3637-09WB
P3637-20WB

CLOSE-TO-CEILING

P7384-30WB p.16



P3675-09WB p.16



OTHER FINISHES

P3675-30WB

P3910-09 p.16



OTHER FINISHES

P3910-09WB

P3911-09 p.16



OTHER FINISHES

P3911-09WB

P3408-30WB p.17



OTHER FINISHES

P3408-09WB
P3408-20WB

P3410-09WB p.17



OTHER FINISHES

P3410-20WB
P3410-30WB

P3360-09 p.18



OTHER FINISHES

P3360-20

P3361-09 p.18



OTHER FINISHES

P3361-20

P3362-09 p.18



OTHER FINISHES

P3362-20

P3363-09 p.18



OTHER FINISHES

P3363-20

CEILING FANS & LIGHT KITS

P2659-09 p.21



OTHER FINISHES

P2659-20

P2660-09 p.21



OTHER FINISHES

P2660-20

P2620-30EBWB p.21



OTHER FINISHES

P2531-09

P2658-09WB p.22



OTHER FINISHES

P2658-20WB

P2621-30EBWB p.22



OTHER FINISHES

P2621-09EBWB

P2602-20EBWB p.22



OTHER FINISHES

P2602-09EBWB

P2602-30EBWB

BATH

P3190-09EBWB p.24



P3191-09EBWB p.24



P3192-09EBWB p.24



P3193-09EBWB p.24



P3052-09EBWB p.24



P3053-09EBWB p.24



P3054-09EBWB p.24



P2706-09EBWB p.25



P2707-09EBWB p.25



P2708-09EBWB p.25



P2709-09EBWB p.25



OUTDOOR

P6067-3130K9 p.27



P6068-3130K9 p.27



P6069-3130K9 p.27



P6076-3130K9 p.27



P6527-3130K9 p.27



P6427-3130K9 p.27



P6526-3130K9 p.28



P6056-3130K9 p.28



P6057-3130K9 p.28



P6059-3130K9 p.28



P6524-2030K9 p.29



P6084-2030K9 p.29



P6085-2030K9 p.29



P6424-2030K9 p.29



P6017-2030K9 p.30



OTHER FINISHES

OTHER FINISHES

OTHER FINISHES

OTHER FINISHES

P6524-3130K9

P6084-3130K9

P6085-3130K9

P6424-3130K9

P5749-2030K9 p.30



P5750-2030K9 p.30



P5751-2030K9 p.30



P5024-0930K9 p.31



P5723-1430K9 p.31



OTHER FINISHES

OTHER FINISHES

P5024-2030K9

P5273-7130K9
5273-8130K9

P550010-031-30 p.32



P560034-031-30 p.32



P560000-031-30 p.32



P6626-31 p.33



P6628-31 p.33



OUTDOOR

P6627-31 p.33



P6629-31 p.33



P6539-31 p.33



P6439-31 p.33



P6630-31 p.34



P6631-31 p.34



P6632-31 p.34



P6633-31 p.34



P6540-31 p.34



P6440-31 p.34



P6619-31 p.35



P6620-31 p.35



P6621-31 p.35



P6622-09 p.35



P6538-31 p.35



P6438-31 p.35



P6634-31 p.36



P6635-31 p.36



P6636-31 p.36



P6637-31 p.36



P6541-31 p.36



P6441-31 p.36



P5980-97 p.37



P5981-97 p.37



P5982-97 p.37



OUTDOOR

P6607-97 p.37



P6503-97 p.37



P6403-97 p.37



P5875-31WB p.38



OTHER FINISHES

P5875-20WB

P5686-108 p.38



OTHER FINISHES

P5686-31

P5861-3130K9 p.38



P3883-2030K9 p.39



OTHER FINISHES

P3883-2030K9

P5862-2030K9 p.39



OTHER FINISHES

P5862-3130K9

P5863-2030K9 p.39



OTHER FINISHES

P5863-3130K9

P5864-2030K9 p.39



OTHER FINISHES

P5864-3130K9

P5445-2030K9 p.39



OTHER FINISHES

P5445-3130K9

P6430-2030K9 p.40



OTHER FINISHES

P6430-3130K9

P6530-2030K9 p.40



OTHER FINISHES

P6530-3130K9

P6077-2030K9 p.40



OTHER FINISHES

P6077-3130K9

P6078-2030K9 p.40



OTHER FINISHES

P6078-3130K9

P6079-2030K9 p.40



OTHER FINISHES

P6079-3130K9

P5864-31WB p.41



OTHER FINISHES

P5864-20WB

P3883-31WB p.41



OTHER FINISHES

P3883-20WB

P5862-31WB p.41



OTHER FINISHES

P5862-20WB

P5863-31WB p.41



OTHER FINISHES

P5863-20WB

P5766-09 p.42



OTHER FINISHES

P5766-20

P5770-09 p.42



OTHER FINISHES

P5770-20

P5772-09 p.42



OTHER FINISHES

P5772-20

P5986-09 p.42



OTHER FINISHES

P5986-20
P5986-31

P5985-09WB p.42



OTHER FINISHES

P5985-20WB
P5985-31WB

OUTDOOR

P5800-09 p.43



OTHER FINISHES

P5800-20

P5801-09 p.43



OTHER FINISHES

P5801-20

P5806-09 p.43



OTHER FINISHES

P5806-20

P5800-0930K9 p.44



OTHER FINISHES

P5800-12930K9

P5801-0930K9 p.44



OTHER FINISHES

P5801-12930K9

P5806-0930K9 p.44



OTHER FINISHES

P5806-12930K9

P6536-2030K9 p.45



OTHER FINISHES

P6536-13630K9

P5676-2030K9 p.45



OTHER FINISHES

P5676-13630K9

P5551-8230K9 p.46



OTHER FINISHES

P5551-2030K9

P5535-8230K9 p.46



OTHER FINISHES

P5535-2030K9

P5622-8230K9 p.46



OTHER FINISHES

P5622-2030K9

P5623-8230K9 p.46



OTHER FINISHES

P5623-2030K9

P560029-031-030 p.47



OTHER FINISHES

P560029-028-30
P560029-129-030

P560030-129-30 p.47



OTHER FINISHES

P560030-031-30

P5774-20/30K p.48



OTHER FINISHES

P5774-3030K9
P5774-3130K9
P5774-8230K9

P5674-20/30K p.48



OTHER FINISHES

P5674-30/30K
P5674-31/30K
P5674-82/30K

P5675-20/30K p.48



OTHER FINISHES

P5675-30/30K
P5675-31/30K
P5675-82/30K

P5741-20/30K p.49



OTHER FINISHES

P5741-30/30K
P5741-31/30K
P5741-82/30K

P5641-20/30K p.49



OTHER FINISHES

P5641-30/30K
P5641-31/30K
P5641-82/30K

P5642-20/30K p.49



OTHER FINISHES

P5642-30/30K
P5642-31/30K
P5642-82/30K

P5643-20-30K p.50



OTHER FINISHES

P5643-30-30K
P5643-31-30K
P5643-82-30K

P5644-20-30K p.50



OTHER FINISHES

P5644-30-30K
P5644-31-30K
P5644-82-30K

P5634-2030K9 p.52



OTHER FINISHES

P5634-3130K9
P5634-8230K9

P5635-2030K9 p.52



OTHER FINISHES

P5635-3130K9
P5635-8230K9

P5736-09 p.53



OTHER FINISHES

P5736-129

OUTDOOR

P560001-129-30 p.53



OTHER FINISHES

P560001-135-30

P3647-3030K9 p.54



OTHER FINISHES

P3647-3130K9

P3648-3030K9 p.54



OTHER FINISHES

P3648-3130K9

P3649-3030K9 p.54



OTHER FINISHES

P3649-3130K9

P3650-3030K9 p.54



OTHER FINISHES

P3650-3130K9

P3665-2030K9 p.55



OTHER FINISHES

P3665-3130K9

P3673-2030K9 p.55



OTHER FINISHES

P3673-3130K9

P5915-16 p.55



OTHER FINISHES

P5915-20

P5821-20 p.56



OTHER FINISHES

P5821-31

P5843-30WB p.56



OTHER FINISHES

P5843-31WB

P5816-30WB p.56



OTHER FINISHES

P5816-31WB

P6077-2030K9 p.56



OTHER FINISHES

P5881-31WB

MLS13GUWW p.57



OTHER FINISHES

MLS18GUWW
MLS26GUWW

E10A19DLED927/JA8 p.57



PTORK3010 p.57



SCONCES

P560001-129-30 p.59



OTHER FINISHES

P560001-135-30

P7188-30WB p.59



P7026-30 p.59



P5914-20 p.59



OTHER FINISHES

P5914-16

P7081-20 p.60



OTHER FINISHES

P7081-09

P7082-20 p.60



OTHER FINISHES

P7082-09

P7052-20EB p.60



OTHER FINISHES

P7052-09EB

CHANDELIERS & PENDANTS

P5108-09EBWB p.62



P5113-09EBWB p.63



P4440-09EBWB p.63



P4441-09EBWB p.63



P3914-09EBWB p.63





Shown: P2503-20, Ceiling Fan



Shown: P5862-31WB, Westport Outdoor
(Image: Toll Brothers)



Shown: P7052-20EB, Sconce



PROGRESS
LIGHTING™

701 Millennium Boulevard
Greenville, SC 29607
progresslighting.com

