



KICHLER.

Have you ever looked at a room in your home and thought, "it just needs something?" Lighting from Kichler is that essential ingredient that transforms "just okay" into something inspiring. Step inside our Interior Collections, and you'll see opportunities for true personal expression. You'll discover bold chandeliers, stylish pendants and unique wall sconces that are sleek and attention-getting...smart collections designed around the trends...and new finishes that are making a rousing comeback. (Brass? Yes, really!) Then, turn on a Kichler light, and watch your room transform even more. See your living space more clearly... make the sofa look a little cozier...bring warmth to the nighttime hours. Can a light fixture do all that? When it's by Kichler, it's designed to inspire your senses and so much more.

With thousands of choices and hundreds' of lighting family options, we want you to experience your home your way. Our collections coordinate from room-to-room, or let you mix and match from wall-to-ceiling. And each fixture is designed to deliver a stunning quality of light that makes your space more beautiful – and more livable.

Your home. Thousands of different Kichler ways to bring it to light.





TABLE OF CONTENTS BY COLLECTION NAME

CONTENT OVERVIEW

- 4** Contents by Collection Name
- 6** Inspiration Gallery
- 16** Visual Index
- 38** Collections
- 318** Pendants & Mini Pendants
- 378** Ceiling Lights & Sconces
- 412** Mirrors
- 414** Bath & Vanity
- 532** Light Bulb Reference & Accessories
- 536** Index
- 546** Legend

CHANDELIER COLLECTIONS | 38

Abellona™ 252-253	Evie 198-199	Parker Point™ 238-241
Ahrendale™ 156-157	Garim™ 50-51	Passport 40-41
Alameda™ 178-179	Grace 254-255	Piper 230-233
Alden 48	Granby™ 290-291	Realta 68-69
Aleeka™ 70-71	Grand Bank™ 138-141	Rocklyn™ 116-117
Ansonia™ 312-313	Grayson 180-183	Rosalie 246-248
Armida™ 300-301	Hayman Bay™ 162-163	Roswell™ 72-77
Armstrong 42-43	Hendrik™ 204-209	Rumer™ 118-119
Aubrey 296-297	Imogen 210-211	Saldana™ 218-219
Berra™ 114	Industrial Cage 122-123	Salem™ 317
Birkdale™ 244-245	Jardine 224-225	Savanna 249
Braelyn™ 120-121	Jasper 78-79	Serina 288-289
Brinley™ 130-135	Jolie 306-307	Shailene 108-109
Cahoon™ 148-151	Jules™ 243	Shelsley™ 250-251
Caldella™ 172-175	Kailey™ 220-221	Signata™ 184-191
Camera™ 286-287	Kayde™ 115	Silberne™ 136-137
Casilda™ 256-261	Kearn™ 168-169	Silver Coral 222-223
Caterham™ 176-177	Keiran 298-299	Stella™ 100-101




CONNECT WITH US

 Become a fan of Kichler Lighting at: [facebook.com, search Kichler Lighting](https://www.facebook.com/kichlerlighting)

 Follow us on twitter at: twitter.com/kichlerlight

 Find us on Pinterest at: <http://pinterest.com/kichlerstyle/>

 Join us on Houzz at: <http://www.houzz.com/pro/kichlerlighting/kichler>

 Watch us on [youtube.com/KichlerLighting](https://www.youtube.com/KichlerLighting)

- Charles** 49
- Circolo** 200-203
- Cirus™** 58-61
- City Lights™** 94-95
- City Loft™** 80-83
- Clague™** 146-147
- Colerne™** 142-145
- Crystal Persuasion™** 234-237
- Crystal Skye™** 226-227
- Cullen** 64-67
- Danika** 44-47
- Daria** 125
- Dover™** 314-316
- Eileen™** 102-107
- Emile** 228-229
- Emory** 192-197
- Erzo™** 96-99
- Evan™** 152-155

- Kensington™** 276-277
- Kimblewick™** 158-161
- Krasi™** 212-213
- Lacey™** 270-275
- Langford™** 292-293
- Lara™** 264-269
- Leanora™** 242
- Leighton™** 262-263
- Lilah** 304-305
- Lucien™** 126-127
- Lucille** 54-57
- Maclain** 62-63
- Monroe™** 278-285
- Moxie** 216-217
- Nicholson™** 308-309
- Olsay™** 92-93
- Olympia™** 294-295
- Organique™** 164-167

- Structures™** 90-91
- Suspension™** 88-89
- Taulbee™** 170-171
- Telford™** 310-311
- Tinley** 124
- Titus** 110-113
- Tremba™** 214-215
- Triad™** 84-87
- Vance** 52-53
- Wedgeport™** 302-303
- Westington™** 128-129
- Wynberg™** 317

To find an Authorized Dealer, visit: www.kichler.com

PENDANTS | 318

LED MINI PENDANTS | 360

MINI PENDANTS | 362

RAIL LIGHTS | 374

CEILING LIGHTS | 378

WALL SCONCES | 394

MIRRORS | 412

Ceiling 382-389
Directional Rail Lights 376-377
Energy Efficient Ceiling 390-393
Energy Efficient Sconces 407-410

BATH & VANITY | 414

Ansonia™ 524
Armida™ 515-517
Aubrey 497-499
Bath & Vanity 526-529
Bazely™ 456-457
Bellamy™ 470-471
Braelyn™ 431-433
Calleigh™ 438
Camerena™ 482-483
Caparros™ 466-467
Casilda™ 444-445
Como™ 453
Contessa 421
Contessa LED 420
Cora 473
Crescent View™ 492
Currituck™ 480-481
Cylinders 477
Lilah 500-502
Linear Bath Energy Efficient 531
Marana™ 450-451
Metro Park™ 459
Millwright™ 430
Monroe™ 484-487
Nicholson™ 520-521
Nita LED 416
Nobu™ Energy Efficient 530
O'Hara 458
Pocelona™ 472
Santiago Energy Efficient 493
Selene™ 452
Serina 508-509
Shailene 503-505
Signata™ 434-435
Souldern 442
Stelata™ 448-449



LED Ceiling 380-381
LED Directional Rail Lights 374-375
LED Wall Sconces 404-406
Mirrors 412-413
Wall Sconces 394-403

Dover™ 523
Drapes 489
Eileen™ 494-496
Freeport™ 425
Freeport™ LED 424
Granby™ 468-469
Hendrik™ 439-441
Impello LED 426
Jardine 429
Jasper 436-437
Jolie 512-514
Keiran 506-507
Keo™ 461
Lacey™ 446-447
Landi LED 422-423
Langford™ 510-511
Largo LED 428
Legé™ 476
Structures™ 464-465
Suspension™ 462-463
Telford™ 519
Telford™ Energy Efficient 518
Tori LED 427
Trinsic™ LED 417
Tubes™ 460
Tully™ 454-455
Uptown 475
Urban Ice™ 443
Wall Sconce Energy Efficient 528
Wedgeport™ 522
Wellington Square 478-479
Wharton™ 474
Willowmore 490-491
Wilton™ 488
Zolon LED 418-419

INSPIRATION GALLERY



CIRUS™ COLLECTION page 58. Get inspired by the warm woods and soft curving panels that defined decor in the late 1940s and 50s. The mid-century modern style features auburn stained wood that pairs well with brushed nickel finishes.



CITY LOFT™ COLLECTION page 80. The name speaks to wide-open spaces; the look carries a soft, modern vibe. Pendants feature adjustable arms for added personalization. Stack or stagger them in a variety of ways.



CAPARROS™ COLLECTION page 466. Why should a bath vanity get all of the attention? Many of our bath collections – like this coastal inspired offering – include pendants and chandeliers to add light as well as interest.



SIGNATA™ COLLECTION page184. This circular design comes to life with curved, crystal-clear glass paneling that gives each piece a glamorous shine. The Natural Brass finish adds warmth, for a soft, contemporary style statement.



CAHOON™ COLLECTION page148. Rustic style and clean lines combine against a soft two-tone finish of Distressed Antique Gray and Anvil Iron.



KIMBLEWICK™ COLLECTION page158. With this rustic farmhouse style, textures abound – including weathered metal framework, Distressed Antique White center column and parchment glass teardrops.



ARMSTRONG COLLECTION page 42. The 1950s space race ushered in decorating pieces that skewed traditional lines. Orbs and satellites serve as the inspiration behind this sputnik-style chandelier. Adjustable arms allow for personalization.



CEILING FAN CATALOG K416 Kichler offers inspiring designs, finishes and details throughout our entire collection of ceiling fans. To view our extensive offering, visit kichler.com or request our Ceiling Fan Collections catalog K416.



LIGHTING SYSTEMS CATALOG For a residential kitchen or bath...home office... new restaurant...or a unique boutique... Kichler Lighting Systems can highlight the finest features. Visit kichler.com to see our Cabinet Lighting/Lighting Systems supplements and catalogs.



OUTDOOR LIGHTING CATALOG K816 Enhance your home's curb appeal with our extensive collection of distinctive outdoor lighting in a variety of styles. See more at kichler.com or request an Outdoor Lighting catalog K816.

CHANDELIER VISUAL INDEX



Abellona™
252



Ahrendale™
156



Alameda™
178



Alden
48



Aleeka™
70



Ansonia™
312



Armida™
300



Armstrong
42



Aubrey
296



Berra™
114



Birkdale™
244



Braelyn™
120



Brinley™
130-135



Cahoon™
148-151



Caldella™
172-175



Camerena™
286



Casilda™
256-261



Caterham™
176



Charles
49



Circolo
200-203



Cirrus™
58-61



City Lights™
94



City Loft™
80-83



Clague™
146



Colerne™
142-145



Crystal Persuasion™
234-237



Crystal Skye™
226



Cullen
64-67



Danika
44-47



Daria
125



Dover™
314-316



Eileen™
102-107



Emile
228



Emory
192-197



Erzo™
96-99



Evan™
152-155



Evie
198



Garim™
50



Grace
254



Granby™
290

CHANDELIER VISUAL INDEX



Grand Bank™
138-141




Grayson
180



Hayman Bay™
162



Hendrik™
204-209



Imogen
210



Industrial Cage
122



Jardine
224



Jasper
78



Jolie
306



Jules™
243



Kailey™
220



Kayde™
115



Kearn™
168



Keiran
298



Kensington™
276



Kimblewick™
158-161



Kradi™
212



Lacey™
270-275



Langford™
292



Lara™
264-269



Leanora™
242



Leighton™
262



Lilah
304



Lucien™
126



Lucille
54-57



Maclain
62



Monroe™
278-285



Moxie
216



Nicholson™
308



Olsay™
92



Olympia™
294



Organique™
164-167



Parker Point™
238-241



Passport
40



Piper
230-233



Realta
68



Rocklyn™
116



Rosalie
246-248



Roswell™
72-77



Rumer™
118

CHANDELIER VISUAL INDEX



Saldana™
218



Salem™
317



Savanna
249



Serina
288



Shailene
108



Shelsley™
250



Signata™
184-191



Silberne™
136



Silver Coral
222



Stella™
100



Structures™
90



Suspension™
88



Taulbee™
170



Telford™
310



Tinley
124



Titus
110-113



Tremba™
214



Triad™
84-87



Vance
52



Wedgeport™
302



Westington™
128



Wynberg™
317

PENDANTS VISUAL INDEX



Ahrendale™
156



Aidan
339



Alameda™
178



Ansonia™
312



Armida™
300



Aubrey
296



Brinley™
130-135



Cahoon™
148-151



Camerena™
286



Cartone™
343



Casilda™
256-261



Caterham™
176



Ceiling
354



Ceiling
355



Charles
49



Cirrus™
58-61



City Loft™
80-83, 336



Clague™
146



Cobson™
329-331



Colerne™
142-145



Crystal Persuasion™
234-237



Crystal Skye™
226



Cullen
64-67



Danika
44-47

PENDANTS VISUAL INDEX



Daria
125



Dover™
314-316



Drum Shades
350



Eileen™
102-107



Emile
228



Emory
192-197



Everly™
320-327



Evie
198



Garim™
50



Granby™
290



Hatteras Bay™
332-335



Hendrik™
204-209



Imogen
210



Indoor/Outdoor
357



Indoor/Outdoor
358



Indoor/Outdoor
359



Industrial Cage
122



Jardine
224



Jolie
306



Keiran
298



Kensington™
276



Lacey™
270-275



Langford™
292



Lara™
264-269



Larkin™
340



Leighton™
262



Lilah
304



Lucille
54-57



Maclain
62



Monroe™
278-285



Moxie
216



Nicholson™
308



Olympia™
294



Pendants
344



Pendants
345



Pendants
346



Pendants
347



Pendants
348



Pendants
349



Pendants
352



Pendants
353



Pendants
356



Piper
230-233



Rocklyn™
116



Roswell™
72-77



Savanna
249



Serina
288



Shelsley™
250

PENDANTS VISUAL INDEX



Silberne™
136, 328



Silver Coral
222



Sloane
342



Structures™
90



Taulbee™
170



Telford™
310



Tinley
124



Titus
110-113



Tremba™
214



Triad™
84-87



Vance
52



Wedgeport™
302



Westington™
128



Wynberg™
317

MINI PENDANTS VISUAL INDEX



Ahrendale™
156, 365



Annata™
363



Ansonia™
312



Aquilino™
363



Armida™
300



Aubrey™
296



Avery™
368



Berra™
114



Braelyn™
120



Brinley™
130-135, 365



Camerena™
286



Casilda™
256-261, 373



Cirrus™
58-61, 372



Crystall Ball™
370



Crystal Skye™
226, 373



Danika™
44, 371



Daria™
125



Devin™
364



Dover™
314-316



Eileen™
102-107



Evie™
198, 373



Granby™
290



Hendrik™
204-209



Holbrook™
367

MINI PENDANTS VISUAL INDEX



Imogen
210



Industrial Cage
122, 364



Jolie
306



Kailey™
220



Kayde™
115



Keiran
298



Kensington™
276



Kinny™
363



Krasi™
212, 372



Lacey™
270-275, 372



Langford™
292



Lara™
264-269



Leighton™
262, 373



Lilah
304



Maclain
62



Modena™
371



Monroe™
278-285



Nicholson™
308



Passport
40



Penelope
366



Realta
68



Reynes™
371



Rocklyn™
116, 365



Roswell™
72-77



Rumer™
118, 365



Serina
288



Shailene
108



Signata™
184-191



Silver Coral
222



Stella™
100



Telford™
310



Tremba™
214, 372



Wedgeport™
302



Westington™
128, 365



Wynberg™
317

WALL SCONCES VISUAL INDEX



Abellona™
253, 402



Ahrendale™
157



Alameda™
179



Alden™
48, 397



Ansonia™
313, 524



Armida™
301, 515-517



Aubrey
296, 497-499



Bath & Vanity
525-529



Bazely™
456



Bellamy™
470-471



Braelyn™
121, 431-433



Brinley™
130-135



Cahoon™
148-151, 398



Caldella™
172-175



Calleigh™
438



Camerena™
287, 403, 482-483



Casilda™
256-261, 402, 444-445



Caterham™
177



Circolo
200-203



Cirrus™
58-61



City Lights™
94, 399



City Loft™
80-83, 397



Colerne™
142-145, 401



Contessa
421



Cora
473



Crystal Persuasion™
234-237



Crystal Skye™
226



Currituck™
480-481



Cylinders
477



Doncaster™
397



Dover™
314-316, 523



Eileen™
102-107, 494-496



Emile
229



Emory
192-197, 403



Evan™
152-155



Freeport™
398, 425



Granby™
291, 399, 468-469



Grand Bank™
138-141



Grayson
180-183, 398



Hendrik™
204-209, 439-441



Industrial Cage
123, 401



Jardine
225, 429



Jasper
78-79, 399, 436-437



Jolie
307, 512-514



Kayde™
115, 400



Keiran
299, 506-507



Kensington™
277, 401



Keo™
461

WALL SCONCES VISUAL INDEX



Kradi™
213



Lacey™
270-275, 446-447



Langford™
293, 510-511



Lara™
264-269, 403



Legé™
476



Leighton™
263, 402



Lilah
304, 500-502



Lucille
54-57



Marana™
450-451



Marchesa™
401



Millwright™
430



Mona
396



Monroe™
278-285, 403, 484-487



Nicholson™
308, 520-521



O'Hara™
458



Parker Point™
238-241, 402



Passport
40, 397



Piper
230-233, 402



Pocelona™
472



Realta
68



Roswell™
72-77



Rumer™
119



Selene™
452



Serina
289, 508-509



Shailene
109, 503-505



Shelsley™
251



Signata™
184-191, 434-435



Silberne™
136-137



Souldern
442



Stelata™
449



Structures™
91, 464-465



Taulbee™
171



Telford™
311, 519



Titus
110-113



Tully™
454-455



Urban Ice™
443



Vance
52, 398



Wedgeport™
303, 522



Westington™
129



Wharton™
474



Wynberg™
317

BATH & VANITY VISUAL INDEX



Ansonia™
524



Armida™
515-517



Aubrey
497-499



Bath & Vanity
525



Bath & Vanity
526



Bath & Vanity
527



Bath & Vanity
528



Bath & Vanity
529



Bazely™
456-457



Bellamy™
470-471



Braelyn™
431-433



Calleigh™
438



Camerena™
482-483



Caparros™
466-467



Casilda™
444-445



Como™
453



Contessa
421



Contessa LED
420



Cora
473



Crescent View™
492



Currituck™
480-481



Cylinders
477



Dover™
523



Drapes
489



Eileen™
494-496



Freeport™
425



Freeport™ LED
424



Granby™
468-469



Hendrik™
439-441



Impello™ LED
426



Jardine
429



Jasper
436-437



Jolie
512-514



Keiran
506-507



Keo™
461



Lacey™
446-447



Landi LED
422-423



Langford™
510-511



Largo LED
428



Legé™
476



Lilah
500-502



Linear Bath EE
531



Marana™
450-451



Metro Park™
459



Millwright™
430



Monroe™
484-487



Nicholson™
520-521



Nita LED
416

BATH & VANITY VISUAL INDEX



Nobu™ EE
530



O'Hara
458



Pocelona™
472



Santiago EE
493



Selene™
452



Serina
508-509



Shailene
503-505



Signata™
434-435



Souldern
442



Stelata™
448-449



Structures™
464-465



Suspension™
462-463



Telford™
519



Telford™ EE
518



Tori LED
427



Trinsic™ LED
417



Tubes™
460



Tully™
454-455



Uptown
475



Urban Ice™
443



Wall Sconce EE
528



Wedgeport™
522



Wellington Square
478-479



Wharton™
474



Willowmore
490-491



Wilton™
488



Zolon LED
418-419



BATH & VANITY SECTION Can be found on page 414.

ENERGY EFFICIENT VISUAL INDEX



Arcola
410



Ceiling
385



Ceiling
390



Ceiling
391



Ceiling
392



Ceiling
393



Energy Efficient
530



Freeport™
409



Jervis™
409



Linear Bath
531



Newport™
410



Nobu™
410, 530



Rigel
408



Santiago
408, 493



Telford™
409, 518



Wall Sconces
407



Wall Sconces
528



Wedgeport™
302-303, 409

ENERGY STAR



Kichler Lighting has been a proud sponsor of the Energy Star Program since 2002. In conjunction with the new Energy Star V2.0 standard, we are making improvements to our assortment of

qualified products. As they are qualified, Energy Star will post them to their website. Please consult the Energy Star website at www.energystar.gov for our current assortment of qualified products, in addition to Kichler.com.

LED VISUAL INDEX



Ceiling LED
380



Ceiling LED
381



Cesya™ LED
406



Contessa LED
420



Freeport™ LED
424



Impello LED
426



Landi LED
422-423



Largo LED
428



LED Rail Lights
375



Mini Pendant LED
361



Mini Pendant LED
361



Nita LED
416



Sedo™ LED
406



Tori LED
427



Trinsic™ LED
417



Wall Sconces LED
404




Zolon LED
418-419

COLLECTIONS

INSPIRED & ENTICING

When outfitting a large space or an entire home with lighting, our motto is simple: start at the center and work your way out. Our Collections give you that all-important focal point – the chandelier – but also include everything else you need to light adjoining spaces. Sconces, pendants, ceiling fixtures ensure total coordination. With a Kichler Collection, you get so much more than just the centerpiece – you get the entire room.





Savanna Pendant 43451 SGD | Page 249 & Rosalie Chandelier 43805 SGD | Page 247



Passport™ Pendant 43761 NI & Wall Sconce 43762 NI | Page 41

PASSPORT™

BRUSHED NICKEL FINISH AND
LIGHT MAPLE STAINED WOOD FINISH WITH
SATIN ETCHED CASED OPAL GLASS



A | 43761 NI
Mini Pendant



B | 43762 NI
Wall Sconce



C | 43760 NI
Linear Chandelier



D | 43759 NI
Linear Chandelier

PASSPORT™

	ITEM #	FINISH	INCAND. BULB	W	H	OVRLL. H	L	EXT.	HCWO	NOTES
A	43761	NI	(1) 60W (C)	3	16.5	91	5.5	---	---	
B	43762	NI	(1) 60W (C)	5.5	16	---	---	4.25	12.75	
C	43760	NI	(5) 60W (C)	4	10.75	84.75	42	---	---	
D	43759	NI	(3) 60W (C)	4	10.75	84.25	32	---	---	

Measurements shown in inches. U.S. & Canada Patent Pending.



Armstrong Chandelier 43119 NBR | Page 43

ARMSTRONG

NATURAL BRASS FINISH



A | 43119 NBR
Chandelier



B | 43118 NBR
Chandelier



Shown Vertically



Shown Horizontally

ARMSTRONG

	ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXT.	HCWO	NOTES
A	43119	NBR	(10) 100W (G40)	39	32	53	62	36	Additional stem 2999. Infinite adjustability from vertical to horizontal.
B	43118	NBR	(8) 100W (G40)	30	26	53	62	36	Additional stem 2999. Infinite adjustability from vertical to horizontal.

Measurements shown in inches. U.S. & Canada Patent Pending.



Danika Linear Chandelier 43680 WH | Page 46 & Mini Pendant 43682 WH | Page 47

DANIKA

WHITE FINISH WITH
LIGHT WOOD ACCENTS



A | 43680 WH
Linear Chandelier



B | 43683 WH
Pendant



C | 43682 WH
Mini Pendant


DANIKA

	ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	L	STEM TILT	EXTRA WIRE	CHAIN/STEM	NOTES
A	43680	WH	(3) 100W (M)	7.25	14.5	53	36.25	90°	74	36	☑ (23-30W CFL) Add. stems 2999 (12") WH. G Type lamp recommended.
B	43683	WH	(1) 100W (M)	16.25	9.25	115	---	---	---	---	☑ (23-30W CFL) G Type lamp recommended.
C	43682	WH	(1) 100W (M)	5.25	9.25	115	---	---	---	---	☑ (23-30W CFL) G Type lamp recommended.

Measurements shown in inches. U.S. & Canada Patent Pending.

DANIKA


WHITE FINISH WITH
LIGHT WOOD ACCENTS



DANIKA

	ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	L	STEM TILT	EXTRA WIRE	CHAIN/STEM	NOTES
A	43680	WH	(3) 100W (M)	7.25	14.5	53	36.25	90°	74	36	(23-30W CFL) Add. stems 2999 (12") WH. G Type lamp recommended.

Measurements shown in inches. U.S. & Canada Patent Pending.



B | 43682 WH
Mini Pendant



C | 43683 WH
Pendant

DANIKA

	ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	NOTES
B	43682	WH	(1) 100W (M)	5.25	9.25	115	(23-30W CFL) G Type lamp recommended.
C	43683	WH	(1) 100W (M)	16.25	9.25	115	(23-30W CFL) G Type lamp recommended.

Measurements shown in inches. U.S. & Canada Patent Pending.

ALDEN

NATURAL BRASS FINISH



B | 43363 NBR
Wall Sconce



A | 43362 NBR
Linear Chandelier



**VINTAGE
FILAMENT
BULB**

SOLD SEPARATELY
40W Candelabra Base
5971 CLR

ALDEN

	ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	L	EXTRA WIRE	CHAIN/ STEM	EXT.	HCWO	NOTES
A	43362	NBR	(6) 60W (C)	11	17.5	92	38.5	63	72	---	---	Additional stem 2999 (12") NBR.
B	43363	NBR	(1) 60W (C)	5	11.5	---	---	---	---	5.25	3.75	

Measurements shown in inches. U.S. & Canada Patent Pending.

CHARLES

NATURAL BRASS FINISH



CHARLES

	ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/STEM	NOTES
A	43276	NBR	(4) 100W (M)	20.5	13.25	52	65	36	☑ (23-30W CFL) Additional stem 2999 (12") NBR.
B	43275	NBR	(2) 100W (M)	12	13.75	52	65	36	☑ (23-30W CFL) Additional chain 2996 NBR, additional stem 2999 (12") NBR. Sloped ceiling kit included.

Measurements shown in inches. U.S. & Canada Patent Pending.

GARIM™

POLISHED NICKEL FINISH
WITH CLEAR GLASS



Shown with Optional
Vintage Filament Bulb
5971 CLR



A | 42474 PN
Chandelier

Shown with Three-light
Clusters Rotated



**VINTAGE
FILAMENT
BULB**

SOLD SEPARATELY
40W Candelabra Base
5971 CLR

GARIM™

ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/STEM	NOTES
A 42474	PN	(9) 40W (C) T Type	33.5	21.75	60	109	36	Additional chain 2996 PN, additional stem 2999 (12") PN. Sloped ceiling kit included.

Measurements shown in inches. U.S. & Canada Patent Pending.

VANCE

NATURAL BRASS FINISH WITH
ANTIQUED MERCURY GLASS



A | 43931 NBR
Linear Chandelier
NOT TO SCALE



VINTAGE
FILAMENT
BULB

SOLD SEPARATELY
40W Candelabra Base
5971 CLR



B | 43934 NBR
Wall Sconce



C | 43933 NBR
Foyer Pendant

VANCE

	ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	L	EXTRA WIRE	CHAIN/STEM	EXT.	HCWO	NOTES
A	43931	NBR	(8) 60W (C)	13.25	24	98	37.25	53	72	---	---	Additional chain 2996 NBR.
B	43934	NBR	(1) 60W (C)	6	16	---	---	---	---	6	8	
C	43933	NBR	(4) 60W (C)	13	30	104	---	50	72	---	---	Additional chain 2996 NBR.

Measurements shown in inches. U.S. & Canada Patent Pending.

LUCILLE

NATURAL BRASS FINISH WITH AUBURN STAINED
WOOD FINISH AND WHITE FABRIC SHADE



A | 43841 NBR
Pendant

Satin Etched
Glass Diffuser



B | 43839 NBR
Chandelier



C | 43843 NBR
Wall Sconce

LUCILLE

ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/STEM	EXT.	HCWO	NOTES
A	NBR	(4) 100W (M)	18.25	20	58	58	36	---	---	☑ (23-30W CFL) Additional stem 2999 (12") NBR.
B	NBR	(3) 60W (C)	24	14.5	53	62	36	---	---	Additional stem 2999 (12") NBR.
C	NBR	(1) 60W (C)	7.75	7	---	---	---	10.5	3.5	

Measurements shown in inches. U.S. & Canada Patent Pending.

LUCILLE

CLASSIC PEWTER FINISH WITH AUBURN STAINED
WOOD FINISH AND WHITE FABRIC SHADE



A | 43841 CLP
Pendant

Satin Etched
Glass Diffuser



B | 43839 CLP
Chandelier



C | 43843 CLP
Wall Sconce

LUCILLE

ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/STEM	EXT.	HCWO	NOTES
A	CLP	(4) 100W (M)	18.25	20	58	58	36	---	---	(23-30W CFL) Additional stem 2999 (12") CLP.
B	CLP	(3) 60W (C)	24	14.5	53	62	36	---	---	Additional stem 2999 (12") CLP. G Type lamp recommended.
C	CLP	(1) 60W (C)	7.75	7	---	---	---	10.5	3.5	


Measurements shown in inches. U.S. & Canada Patent Pending.



Cirus™ Pendant 43754 AUB | Page 61

CIRUS™

BRUSHED NICKEL WITH AUBURN STAINED
WOOD FINISH ACCENTS, WHITE FABRIC SHADE
& SATIN ETCHED GLASS DIFFUSER



A | 43754 AUB
Pendant



B | 43753 AUB
Pendant



C | 43755 AUB
Mini Pendant



D | 43756 AUB
Wall Sconce


CIRUS™

	ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/ STEM	EXT.	HCWO	NOTES
A	43754	AUB	(5) 100W (M)	30	14	---	104	36	---	---	☑ (23-30W CFL) Additional stem 2999 (12") NI and/or additional stem 2997 (24") NI.
B	43753	AUB	(4) 100W (M)	24	12	---	---	36	---	---	☑ (23-30W CFL) Additional stem 2999 (12") NI and/or additional stem 2997 (24") NI.
C	43755	AUB	(1) 100W (M)	8	8.5	47	66	36	---	---	☑ (18-25W CFL) Additional stem 2999 (12") NI and/or additional stem 2997 (24") NI.
D	43756	AUB	(2) 60W (M) ✓	7.5	12	---	---	---	5.5	6	☑ (13-15W CFL)

Measurements shown in inches. U.S. & Canada Patent Pending.

CIRUS™

BRUSHED NICKEL WITH AUBURN STAINED
WOOD FINISH ACCENTS, WHITE FABRIC SHADE
& SATIN ETCHED GLASS DIFFUSER



A | 43755 AUB
Mini Pendant



Shown as
Pendant - 50.25" H.

CONVERTIBLE

Create two distinct lighting
options with one fixture:
Pendant or Semi Flush

B | 43753 AUB



Shown as
Semi Flush - 12.25" H.



C | 43756 AUB
Wall Sconce



Shown as
Pendant - 51" H.

CONVERTIBLE

Create two distinct lighting
options with one fixture:
Pendant or Semi Flush

D | 43754 AUB



Shown as
Semi Flush - 13" H.

CIRUS™

	ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/STEM	EXT.	HCWO	NOTES
A	43755	AUB	(1) 100W (M)	8	8.5	47	66	36	---	---	Ⓜ (18-25W CFL) Additional stem 2999 (12") NI and/or additional stem 2997 (24") NI.
B	43753	AUB	(4) 100W (M)	24	12	---	---	36	---	---	Ⓜ (23-30W CFL) Additional stem 2999 (12") NI and/or additional stem 2997 (24") NI.
C	43756	AUB	(2) 60W (M) ✓	7.5	12	---	---	---	5.5	6	Ⓜ (13-15W CFL)
D	43754	AUB	(5) 100W (M)	30	14	---	104	36	---	---	Ⓜ (23-30W CFL) Additional stem 2999 (12") NI and/or additional stem 2997 (24") NI.

Measurements shown in inches. U.S. & Canada Patent Pending.

MACLAIN

NATURAL BRASS FINISH WITH
SATIN ETCHED WHITE GLASS



A | 43742 NBR
Chandelier Pendant
NOT TO SCALE



B | 43743 NBR
Mini Pendant



Shown as
Pendant - 14" H.

CONVERTIBLE

Create two distinct lighting
options with one fixture:
Pendant or Semi Flush.

C | 43744 NBR



Shown as
Semi Flush - 13" H.


MACLAIN

	ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/STEM	NOTES
A	43742	NBR	(4) 100W (M)	24	24.25	63	39	36	☑ (23-30W CFL) Additional stem 2999 (12") NBR.
B	43743	NBR	(1) 100W (M)	10	12.5	49	60	36	☑ (23-30W CFL) Additional stem 2999 (12") NBR.
C	43744	NBR	(3) 100W (M)	16	11.75	51	56	36	☑ (23-30W CFL) Additional stem 2999 (12") NBR.

Measurements shown in inches. U.S. & Canada Patent Pending.

CULLEN

CLASSIC PEWTER FINISH WITH
POLISHED NICKEL ACCENTS



Adjustable Arms to
create a Linear Look

Polished Nickel Accent

A | 43901 CLP
Linear Chandelier



VINTAGE FILAMENT BULB

SOLD SEPARATELY
40W Candelabra Base
5971 CLR



B | 43900 CLP
Foyer Pendant



C | 43902 CLP
Foyer Pendant

CULLEN

	ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/STEM	NOTES
A	43901	CLP	(13) 60W (C)	38.75	22.25	61	14	36	Additional stem 2999 (12") NI, and/or 2997 (24") NI. G Type lamp recommended.
B	43900	CLP	(5) 60W (C)	14	26.25	65	31	36	Additional stem 2999 (12") NI, and/or 2997 (24") NI.
C	43902	CLP	(5) 60W (C)	18	31.5	71	26	36	Additional stem 2999 (12") NI, and/or 2997 (24") NI.

Measurements shown in inches. U.S. & Canada Patent Pending.

CULLEN

OLDE BRONZE® FINISH WITH
NATURAL BRASS ACCENTS



A | 43901 OZ
Linear Chandelier



VINTAGE FILAMENT BULB

SOLD SEPARATELY
40W Candelabra Base
5971 CLR



B | 43900 OZ
Foyer Pendant



C | 43902 OZ
Foyer Pendant

CULLEN

	ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/STEM	NOTES
A	43901	OZ	(13) 60W (C)	38.75	22.25	61	14	36	Additional stem 2999 (12") OZ. G Type lamp recommended.
B	43900	OZ	(5) 60W (C)	14	26.25	65	31	36	Additional stem 2999 (12") OZ.
C	43902	OZ	(5) 60W (C)	18	31.5	71	26	36	Additional stem 2999 (12") OZ.


Measurements shown in inches. U.S. & Canada Patent Pending.

REALTA

BRUSHED NICKEL FINISH WITH
SATIN ETCHED CASED OPAL GLASS



A | 43687 NI
Linear Chandelier
NOT TO SCALE





B | 43689 NI
Wall Sconce



C | 43688 NI
Mini Pendant



D | 43686 NI
Linear Chandelier

Satin Etched
Cased Opal
Glass

REALTA

	ITEM #	FINISH	INCAND. BULB	W	H	OVRL H	L	EXTRA WIRE	CHAIN/STEM	EXT.	HCWO	NOTES
A	43687	NI	(5) 50W (G9)	11	6.5	44.5	40	102	36	---	---	Additional chain 2996 NI, additional stem 4935 (12") NI. Halogen light source. Sloped ceiling kit included.
B	43689	NI	(1) 50W (G9)	10	5.5	---	---	---	---	5	2.75	Halogen light source.
C	43688	NI	(1) 50W (G9)	7	6.5	45	12	68	36	---	---	Additional stem 2999 (12") NI and/or 2997 (24") NI. Halogen light source.
D	43686	NI	(3) 50W (G9)	10	6.5	44.5	28	107	36	---	---	Additional chain 2996 NI, additional stem 2999 (12") NI and/or 2997 (24") NI. Halogen light source. Sloped ceiling kit included.

Measurements shown in inches. U.S. & Canada Patent Pending.

ALEEKA™

CLASSIC PEWTER FINISH WITH
SATIN ETCHED CASED OPAL GLASS



A | 43366 CLP
Chandelier
NOT TO SCALE



B | 43364 CLP
Chandelier



C | 43365 CLP
Chandelier

ALEEKA™

ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/STEM	NOTES	
A	43366	CLP	(5) 50W (G9)	28.25	31	72	103	36	Add. chain 2996 CLP, add. stem 4935 (12") CLP. Halogen light source. Sloped ceiling kit included.
B	43364	CLP	(3) 50W (G9)	28.25	12.75	53	106	36	Add. chain 2996 CLP, add. stem 2999 (12") CLP. Halogen light source. Sloped ceiling kit included.
C	43365	CLP	(5) 50W (G9)	34	17.25	57	104	36	Add. chain 2996 CLP, add. stem 4935 (12") CLP. Halogen light source. Sloped ceiling kit included.

Measurements shown in inches. U.S. & Canada Patent Pending.

ROSWELL™

OLDE BRONZE® FINISH WITH
OFF-WHITE LINEN FABRIC SHADES &
SATIN ETCHED GLASS DIFFUSER



Inner Gold Tone Highlights

A | 43306 OZ
Large Foyer Pendant
NOT TO SCALE



B | 43304 OZ
Mini Pendant



C | 43303 OZ
Oval Chandelier/Pendant



ROSWELL™

	ITEM #	FINISH	INCAND. BULB	W	H	OVRLL. H	L	EXTRA WIRE	CHAIN/STEM	NOTES
A	43306	OZ	(6) 100W (M)	21.25	45.25	84	---	82	36	① (23-30W CFL) Additional chain 4908 OZ, additional stem 4935 (12") OZ. Sloped ceiling kit included.
B	43304	OZ	(1) 100W (M) ✦	5.25	8.5	49	---	62	36	② (23-30W CFL) Additional chain 2996 OZ, additional stem 2999 (12") OZ. Sloped ceiling kit included. Fixture is open at bottom.
C	43303	OZ	(3) 100W (M)	12.25	8	49	37.25	95	36	③ (23-30W CFL) Additional chain 2996 OZ, additional stem 4935 (12") OZ. Sloped ceiling kit included.

Measurements shown in inches. U.S. & Canada Patent Pending.

ROSWELL™

OLDE BRONZE® FINISH WITH
OFF-WHITE LINEN FABRIC SHADES &
SATIN ETCHED GLASS DIFFUSER



A | 43305 OZ
Wall Sconce
ADA Compliant



Inner Off-White Linen Fabric Shade

B | 43301 OZ
Pendant



Satin Etched Glass Diffuser

C | 43390 OZ
Pendant

ROSWELL™

ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/STEM	EXT.	HCWO	NOTES
A	OZ	(1) 50W (G9)	5	9.5	---	---	---	3.75	4.25	Ⓧ Ⓡ Halogen light source. Fixture is open at bottom.
B	OZ	(3) 100W (M)	18	7.25	49	66	36	---	---	Ⓧ (23-30W CFL) Additional chain 2996 OZ, additional stem 4935 (12") OZ. Sloped ceiling kit included.
C	OZ	(4) 100W (M)	24	9	47	69	36	---	---	Ⓧ (23-30W CFL) Additional chain 2996 OZ, additional stem 4935 (12") OZ. Sloped ceiling kit included.

Measurements shown in inches. U.S. & Canada Patent Pending.

ROSWELL™

BRUSHED NICKEL FINISH WITH
OFF-WHITE LINEN FABRIC SHADE AND
SATIN ETCHED GLASS DIFFUSER



A | 43306 NI
Large Foyer Pendant
NOT TO SCALE

ROSWELL™

	ITEM #	FINISH	INCAND. BULB	W	H	OVRLL. H	EXTRA WIRE	CHAIN/STEM	NOTES
A	43306	NI	(6) 100W (M)	21.25	45.25	84	82	36	① (23-30W CFL) Additional chain 4908 NI, additional stem 4935 (12") NI. Sloped ceiling kit included.

Measurements shown in inches. U.S. & Canada Patent Pending.

ROSWELL™

BRUSHED NICKEL FINISH WITH
OFF-WHITE LINEN FABRIC SHADE &
SATIN ETCHED GLASS DIFFUSER



Inner Off-White Linen Fabric Shade

Satin Etched Glass Diffuser

A | 43303 NI
Oval Chandelier/Pendant
NOT TO SCALE





B | 43304 NI
Mini Pendant



C | 43305 NI
Wall Sconce
ADA Compliant



D | 43390 NI
Pendant



Satin Etched
Glass Diffuser

E | 43301 NI
Pendant

ROSWELL™

	ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	L	EXTRA WIRE	CHAIN/STEM	EXT.	HCWO	NOTES
A	43303	NI	(3) 100W (M)	12.25	7.75	46	37.25	95	36	---	---	☑ (23-30W CFL) Additional chain 2996 NI, additional stem 4935 (12") NI. Sloped ceiling kit included.
B	43304	NI	(1) 100W (M) ❖	5.25	8.5	47	---	62	36	---	---	☑ (23-30W CFL) Additional chain 2996 NI, additional stem 2999 (12") NI and/or 2997 (24") NI. Sloped ceiling kit included.
C	43305	NI	(1) 50W (G9) Ⓛ	5	9.5	---	---	---	---	3.75	4.25	Ⓛ Ⓛ Halogen light source. Fixture is open at bottom.
D	43390	NI	(4) 100W (M)	24	9	47	---	69	36	---	---	☑ (23-30W CFL) Additional chain 2996 NI, additional stem 4935 (12") NI. Sloped ceiling kit included.
E	43301	NI	(3) 100W (M) ❖	18	7.25	49	---	66	36	---	---	☑ (23-30W CFL) Additional chain 2996 NI, additional stem 4935 (12") NI. Sloped ceiling kit included.

Measurements shown in inches. U.S. & Canada Patent Pending.

JASPER

NATURAL BRASS FINISH WITH
SATIN ETCHED CASÉD OPAL GLASS



A | 43580 NBR
Linear Chandelier
NOT TO SCALE



B | 45580 NBR
Wall Sconce

MATCHING BATH

See matching
bath fixtures
on page 437.



JASPER

	ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	L	EXTRA WIRE	CHAIN/ STEM	EXT.	HCWO	NOTES
A	43580	NBR	(5) 50W (G9)	4.5	11.75	40	38.25	72	36	---	---	Additional stem 2999 (12") NBR.
B	45580	NBR	(1) 50W (G9)	4.5	11.5	---	---	---	---	5.75	5.75	

Measurements shown in inches. U.S. & Canada Patent Pending.

JASPER

POLISHED CHROME FINISH WITH
SATIN ETCHED CASÉ OPAL GLASS



A | 43580 CH
Linear Chandelier
NOT TO SCALE



B | 45580 CH
Wall Sconce

MATCHING BATH

See matching bath fixtures on page 436.



JASPER

	ITEM #	FINISH	INCAND. BULB	W	H	OVRL H	L	EXTRA WIRE	CHAIN/STEM	EXT.	HCWO	NOTES
A	43580	CH	(5) 50W (G9)	4.5	11.75	40	38.25	72	36	---	---	Additional stem 2999 (12") CH.
B	45580	CH	(1) 50W (G9)	4.5	11.5	---	---	---	---	5.75	5.75	

Measurements shown in inches. U.S. & Canada Patent Pending.





City Loft™ Pendant 43784 PN & Chandelier/Pendant 43783 PN | Page 82

CITY LOFT™

OLDE BRONZE® FINISH WITH
WHITE OPAL ETCHED GLASSA | 43785 OZ
PendantB | 43787 OZ
Wall SconceC | 43784 OZ
Pendant

Adjustable Arms

Adjustable Arms

D | 43783 OZ
Chandelier/Pendant

CITY LOFT™

ITEM #	FINISH	INCAND. BULB	W	H	OVRLL. H	L	EXTRA WIRE	CHAIN/STEM	EXT.	HCWO	NOTES	
A	43785	OZ	(1) 200W (M)	9	17	55	16.25	38	36	---	---	Ⓜ (30-52W CFL) Additional chain 2996 OZ, additional stem 2999 (12") OZ. Sloped ceiling kit included.
B	43787	OZ	(1) 100W (M)	5.5	17.25	---	---	---	---	4.75	13	ⓂⓃ (23-30W CFL)
C	43784	OZ	(1) 200W (M)	16.25	21.25	60	20.5	30	36	---	---	Ⓜ (30-52W CFL) Additional chain 2996 OZ, additional stem 4935 (12") OZ. Sloped ceiling kit included.
D	43783	OZ	(1) 200W (M)	20.5	25.75	64	25	20	36	---	---	Ⓜ (30-52W CFL) Additional chain 2996 OZ, additional stem 4935 (12") OZ. Sloped ceiling kit included.

Measurements shown in inches. U.S. & Canada Patent Pending.

CITY LOFT™

POLISHED NICKEL FINISH WITH
WHITE OPAL ETCHED GLASS



A | 43787 PN
Wall Sconce



B | 43785 PN
Pendant



C | 43784 PN
Pendant

Adjustable Arms

Adjustable Arms



D | 43783 PN
Chandelier/Pendant

CITY LOFT™

ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	L	EXTRA WIRE	CHAIN/STEM	EXT.	HCWO	NOTES
A	43787	PN	(1) 100W (M)	5.5	17.25	---	---	---	4.75	13	Ⓢ (23-30W CFL)
B	43785	PN	(1) 200W (M)	9	17	55	16.25	38	36	---	Ⓢ (30-52W CFL) Additional chain 2996 PN, additional stem 2999 (12") PN. Sloped ceiling kit included.
C	43784	PN	(1) 200W (M)	16.25	21.25	60	20.5	30	36	---	Ⓢ (30-52W CFL) Additional chain 2996 PN, additional stem 4935 (12") PN. Sloped ceiling kit included.
D	43783	PN	(1) 200W (M)	20.5	25.75	64	25	20	36	---	Ⓢ (30-52W CFL) Additional chain 2996 PN, additional stem 4935 (12") PN. Sloped ceiling kit included.

Measurements shown in inches. U.S. & Canada Patent Pending.

CITY LOFT™

NATURAL BRASS FINISH WITH
WHITE OPAL ETCHED GLASSA | 43785 NBR
PendantB | 43787 NBR
Wall SconceC | 43784 NBR
Pendant

Adjustable Arms

Adjustable Arms

D | 43783 NBR
Chandelier/Pendant

CITY LOFT™

ITEM #	FINISH	INCAND. BULB	W	H	OVRLL. H	L	EXTRA WIRE	CHAIN/STEM	EXT.	HCWO	NOTES	
A	43785	NBR	(1) 200W (M)	9	17	55	16.25	38	36	---	---	Ⓜ (30-52W CFL) Additional chain 2996 NBR, additional stem 2999 (12") NBR. Sloped ceiling kit included.
B	43787	NBR	(1) 100W (M)	5.5	17.25	---	---	---	---	4.75	13	Ⓜ (23-30W CFL) Additional stem 2999 (12") NBR.
C	43784	NBR	(1) 200W (M)	16.25	21.25	60	20.5	30	36	---	---	Ⓜ (30-52W CFL) Additional chain 2996 NBR, additional stem 2999 (12") NBR. Sloped ceiling kit included.
D	43783	NBR	(1) 200W (M)	20.5	25.75	64	25	20	36	---	---	Ⓜ (30-52W CFL) Additional chain 2996 NBR, additional stem 2999 (12") NBR. Sloped ceiling kit included.

Measurements shown in inches. U.S. & Canada Patent Pending.

TRIAD™

CLASSIC PEWTER FINISH WITH
CLEAR OUTER GLASS & WHITE
VETRO MICA GLASS INNER SHADES



GU10
Downlight

A | 42548 CLP
Linear Chandelier



B | 42549 CLP
Pendant



GU10
Downlight

C | 42547 CLP
Linear Chandelier

TRIAD™

	ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	L	EXTRA WIRE	CHAIN/ STEM	NOTES
A	42548	CLP	(3) 100W (M) & (3) 50W (GU10)	11.5	23	61	40	87	36	Ⓜ (23-30W CFL) Additional chain 2996 CLP, additional stem 2999 (12") CLP. Sloped ceiling kit included. 3-way turn switch. Recommended bulb GU10 MR16 LED not included.
B	42549	CLP	(1) 100W (M) & (1) 50W (GU10)	7.75	18	58	12	44	36	Ⓜ (23-30W CFL) Additional chain 2996 CLP, additional stem 2999 (12") CLP. Sloped ceiling kit included. 3-way turn switch. Recommended bulb GU10 MR16 LED not included.
C	42547	CLP	(3) 100W (M) & (3) 50W (GU10)	7.75	18	56	31.25	81	36	Ⓜ (23-30W CFL) Additional chain 2996 CLP, additional stem 2999 (12") CLP. Sloped ceiling kit included. 3-way turn switch. Recommended bulb GU10 MR16 LED not included.

Measurements shown in inches. U.S. Design Patent No.: D713,090.

TRIAD™

OLDE BRONZE® FINISH WITH
CLEAR OUTER GLASS & VETRO
MICA GLASS INNER SHADES





B | 42549 OZ
Pendant



C | 42547 OZ
Linear Chandelier

TRIAD™

ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	L	EXTRA WIRE	CHAIN/STEM	NOTES
A	0Z	(3) 100W (M) & (3) 50W (GU10)	11.5	23	61	40	87	36	⊗ (23-30W CFL) Additional chain 2996 OZ, additional stem 2999 (12") OZ. Sloped ceiling kit included. 3-way turn switch. Recommended bulb GU10 MR16 LED not included.
B	0Z	(1) 100W (M) & (1) 50W (GU10)	7.75	18	58	12	44	36	⊗ (23-30W CFL) Additional chain 2996 OZ, additional stem 2999 (12") OZ. Sloped ceiling kit included. 3-way turn switch. Recommended bulb GU10 MR16 LED not included.
D	0Z	(3) 100W (M) & (3) 50W (GU10)	7.75	18	56	31.25	81	36	⊗ (23-30W CFL) Additional chain 2996 OZ, additional stem 2999 (12") OZ. Sloped ceiling kit included. 3-way turn switch. Recommended bulb GU10 MR16 LED not included.

Measurements shown in inches. U.S. Design Patent No.: D713,090.

SUSPENSION™

BRUSHED NICKEL FINISH WITH
SATIN ETCHED CASED OPAL GLASS

MATCHING BATH

See matching
bath fixtures
on page 462.



A | 42017 NI
Linear Chandelier



B | 42018 NI
Linear Chandelier

SUSPENSION™

ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	L	EXTRA WIRE	CHAIN/STEM	NOTES	
A	42017	NI	(3) 60W (C/K) Ⓢ	4.75	11	43	41	101	36	Additional chain 2996 NI, additional stem 2999 (12") NI and/or 2997 (24") NI. Krypton bulbs included. Height includes one 6" stem. Sloped ceiling kit included.
B	42018	NI	(5) 60W (C/K) Ⓢ	4.25	10.5	43	50.75	98	36	Additional chain 2996 NI, additional stem 2999 (12") NI and/or 2997 (24") NI. Krypton bulbs included. Height includes one 6" stem. Sloped ceiling kit included.

Measurements shown in inches. U.S. Design Patent No. D644,371.

SUSPENSION™

BLACK FINISH WITH
SATIN ETCHED CASED OPAL GLASS



A | 42017 BK
Linear Chandelier



B | 42018 BK
Linear Chandelier

SUSPENSION™

ITEM #	FINISH	INCAND. BULB	W	H	OVRLL. H	L	EXTRA WIRE	CHAIN/STEM	NOTES
A	BK	(3) 60W (C/K)	4.75	11	43	41	101	36	Additional chain 2996 BK, additional stem 2999 (12") BK. Krypton bulbs included. Height includes one 6" stem. Sloped ceiling kit included.
B	BK	(5) 60W (C/K)	4.25	10.5	43	50.75	98	36	Additional chain 2996 BK, additional stem 2999 (12") BK. Krypton bulbs included. Height includes one 6" stem. Sloped ceiling kit included.

Measurements shown in inches. U.S. Design Patent No. D644,371.

STRUCTURES™

BRUSHED NICKEL FINISH WITH
SATIN ETCHED GLASS OR OLDE BRONZE®
FINISH WITH LIGHT UMBER GLASS

COORDINATING CEILING FAN

See the full line of Kichler®
Ceiling Fans in catalog K416
or visit kichler.com.

B | 300009 NI, OZ



A | 2955 NI, OZ
Linear Chandelier



C | 2043 NI
Linear Chandelier

STRUCTURES™

ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	L	STEM TILT	EXTRA WIRE	CHAIN/STEM	EXT.	HCWO	NOTES	
A	2955	NI, OZ	(3) 100W (MNCN)	9	21.5	60	37	45°(12:12)	97	36	---	---	Add. stem 2999 (12") NI, OZ and/or 2997 (24") NI.
B	300009	NI, OZ	---	---	---	---	---	---	---	---	---	---	See the full line of Kichler® Ceiling Fans in catalog K416 or visit kichler.com .
C	2043	NI	(4) 100W (MNCN)	9	21.5	60	47.5	45°(12:12)	96	36	---	---	Add. stem 2999 (12") NI and/or 2997 (24") NI. Halogen light source.
D	6963	NI	(1) 100W (MNCN)	9	7.5	---	---	---	---	---	10.5	2.5	Halogen light source.
E	2667	NI	(1) 100W (MNCN)	18	15	53	---	45°(12:12)	62	36	---	---	Add. stem 2999 (12") NI and/or 2997 (24") NI. Halogen light source.
F	2655	NI	(1) 100W (MNCN)	9	8.5	47	---	45°(12:12)	65	36	---	---	Add. stem 2999 (12") NI and/or 2997 (24") NI. Halogen light source.
G	2055	NI	(5) 100W (MNCN)	30.5	22.5	61	---	45°(12:12)	96	36	---	---	Add. stem 2999 (12") NI and/or 2997 (24") NI. Halogen light source.

Measurements shown in inches. U.S. Patent Design No. D511,858 D512,177: A. No. D512,177: D. U.S. & Canada Patent Pending: E. No. D512,177: F. No. D511,58 D512,177 D564,123: G.



D | 6963 NI
Wall Sconce

MATCHING BATH

See matching
bath fixtures
on page 464.



E | 2667 NI
Pendant



Shown as
Mini Pendant - 8.5" H.

CONVERTIBLE

Create two distinct lighting
options with one fixture:
Mini Pendant or Semi Flush.

F | 2655 NI



Shown as
Semi Flush - 9.5" H.



G | 2055 NI
Chandelier

MATCHING MIRROR

41056 NI
See page 413 or
kichler.com.



OLSAY™

POLISHED CHROME FINISH WITH
SATIN ETCHED CASSED OPAL GLASS



A | 42505 CH
Chandelier



B | 42506 CH
Chandelier

OLSAY™

	ITEM #	FINISH	INCAND. BULB	W	H	OVRLL. H	EXTRA WIRE	CHAIN/STEM	NOTES
A	42505	CH	(3) 50W (G9)	22.5	22.75	61	64	36	Add. chain 2996 CH, add. stem 2999 (12") CH. Halogen light source. Sloped ceiling kit incl.
B	42506	CH	(4) 50W (G9)	28.75	28.75	67	94	36	Add. chain 2996 CH, add. stem 2999 (12") CH. Halogen light source. Sloped ceiling kit incl.

Measurements shown in inches. U.S. & Canada Patent Pending.

OLSAY™

OLDE BRONZE® FINISH WITH
SATIN ETCHED CASED OPAL GLASS



A | 42506 OZ
Chandelier



B | 42505 OZ
Chandelier

OLSAY™

	ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/ STEM	NOTES
A	42506	OZ	(4) 50W (G9)	28.75	28.75	67	94	36	Add. chain 2996 OZ, add. stem 2999 (12") OZ. Halogen light source. Sloped ceiling kit incl.
B	42505	OZ	(3) 50W (G9)	22.5	22.75	61	64	36	Add. chain 2996 OZ, add. stem 2999 (12") OZ. Halogen light source. Sloped ceiling kit incl.


Measurements shown in inches. U.S. & Canada Patent Pending.

CITY LIGHTS™

CLASSIC PEWTER FINISH WITH
SATIN ETCHED CASED OPAL GLASS



A | 42940 CLP
Chandelier
NOT TO SCALE



CITY LIGHTS™

ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	L	EXTRA WIRE	CHAIN/STEM	EXT.	HCWO	NOTES	
A	42940	CLP	(7) 50W (G9)	23.5	23.75	59	25.75	100	36	---	---	Additional chain 2996 CLP, additional stem 4935 (12") CLP. Sloped ceiling kit included. Halogen light source.
B	42942	CLP	(2) 50W (G9)	15.5	16	---	---	---	---	4.5	7.25	Halogen light source.
C	42941	CLP	(7) 50W (G9)	3.5	18.5	54	34.5	100	---	---	---	Additional chain 2996 CLP, additional stem 4935 (12") CLP. Sloped ceiling kit included. Halogen light source.

Measurements shown in inches. U.S. & Canada Patent Pending.



B | 42942 CLP
Wall Sconce



C | 42941 CLP
Linear Chandelier



Side View of
Linear Chandelier

ERZO

NATURAL BRASS FINISH



A | 43857 NBR
Chandelier



VINTAGE FILAMENT BULB

SOLD SEPARATELY
40W Candelabra Base
5971 CLR



B | 43859 NBR
Chandelier

ERZO

	ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/ STEM	NOTES
A	43857	NBR	(8) 60W (C)	35.5	9.25	47.5	104	36	Additional stem 2999 (12") NBR.
B	43859	NBR	(6) 60W (C)	26	9.25	47.5	69	36	Additional stem 2999 (12") NBR.

Measurements shown in inches. U.S. & Canada Patent Pending.

ERZO

SATIN NICKEL FINISH



A | 43857 SN
Chandelier



VINTAGE FILAMENT BULB

SOLD SEPARATELY
40W Candelabra Base
5971 CLR



B | 43859 SN
Chandelier

ERZO

	ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/STEM	NOTES
A	43857	SN	(8) 60W (C)	35.5	9.25	47.5	104	36	Additional chain 2996 SN, additional stem 2999 (12") SN. Sloped ceiling kit included.
B	43859	SN	(6) 60W (C)	26	9.25	47.5	69	36	Additional chain 2996 SN, additional stem 2999 (12") SN. Sloped ceiling kit included.

Measurements shown in inches. U.S. & Canada Patent Pending.

STELLA™

POLISHED CHROME FINISH WITH
SATIN ETCHED CASED OPAL GLASS



A | 42214 CH
Chandelier



B | 42216 CH
Mini Pendant



C | 42213 CH
Chandelier

STELLA™

	ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	STEM TILT	EXTRA WIRE	CHAIN/STEM	NOTES
A	42214	CH	(24) 40W (C)	36	53	91	---	85	36	Additional chain 4901 CH, additional stem 2999 (12") CH. Sloped ceiling kit included.
B	42216	CH	(1) 60W (C)	3.5	16.75	49	45°(12:12)	69	36	Additional stem 2999 (12") CH. Height includes one 6" stem.
C	42213	CH	(9) 60W (C)	26.5	25	63	45°(12:12)	54	36	Additional stem 2999 (12") CH.

Measurements shown in inches. U.S. & Canada Patent Pending.

EILEEN™

POLISHED CHROME FINISH WITH
SATIN ETCHED CASED OPAL GLASS



A | 1894 CH
Mini Chandelier



B | 3497 CH
Mini Pendant



C | 1896 CH
Chandelier



D | 1897 CH
Chandelier




Satin Etched
White Glass

E | 3299 CH
Inverted Pendant

EILEEN™

ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/STEM	NOTES	
A	1894	CH	(3) 100W (M)	18.5	13.75	52	63	36	Ⓜ (23-30W CFL) Additional chain 2996 CH, additional stem 2999 (12") CH. May be installed with glass up or down. Sloped ceiling kit included.
B	3497	CH	(1) 100W (M)	4.5	14	46	68	36	Ⓜ (23-30W CFL) Additional chain 2996 CH, additional stem 2999 (12") CH. Height includes one 6" stem. Sloped ceiling kit included.
C	1896	CH	(5) 100W (M)	24	16.5	55	61	36	Ⓜ (23-30W CFL) Additional chain 2996 CH, additional stem 2999 (12") CH. Sloped ceiling kit included. May be installed glass up or down.
D	1897	CH	(9) 100W (M)	30	28.25	67	95	36	Ⓜ (23-30W CFL) Additional chain 2996 CH, additional stem 2999 (12") CH. Sloped ceiling kit included.
E	3299	CH	(4) 150W (M)	25.75	26.25	65	91	36	Ⓜ (23-30W CFL) Additional chain 2996 CH, additional stem 2999 (12") CH. Sloped ceiling kit included.

Measurements shown in inches.



Satin Etched
White Glass

Shown as
Semi Flush - 13.5" H.

CONVERTIBLE

Create two distinct lighting options
with one fixture: Semi Flush or
Inverted Pendant.

H | 3797 CH



Shown as
Inverted Pendant - 14.5" H.



F | 5096 CH
Wall Sconce



G | 8043 CH
Flush Mount



J | 3898 CH
Linear Chandelier

MATCHING BATH

See matching
bath fixtures
on page 494.



EILEEN™

ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	L	EXTRA WIRE	CHAIN/ STEM	EXT.	HCWO	NOTES	
F	5096	CH	(1) 100W (M)	4.5	10.75	---	---	---	---	7	5.75	Ⓜ (18-25W CFL) May be installed with glass up or down.
G	8043	CH	(1) 100W (M)	5	6.25	---	---	---	---	---	---	Ⓜ (23-30W CFL)
H	3797	CH	(3) 100W (M)	17.25	14.5	53	---	21	36	---	---	Ⓜ (23-30W CFL) Additional chain 2996 CH.
J	3898	CH	(6) 100W (M)	16.25	18.5	57	30	95	36	---	---	Ⓜ (23-30W CFL) Additional chain 2996 CH, additional stem 2999 (12") CH. May be installed with glass up or down. Sloped ceiling kit included.

Measurements shown in inches.

EILEEN™

BRUSHED NICKEL FINISH WITH
SATIN ETCHED CASED OPAL GLASS



A | 1894 NI
Mini Chandelier



B | 3497 NI
Mini Pendant



C | 1896 NI
Chandelier



D | 1897 NI
Chandelier



E | 3299 NI
Inverted Pendant

EILEEN™

ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/STEM	NOTES	
A	1894	NI	(3) 100W (M)	18.5	13.75	52	63	36	Ⓢ (23-30W CFL) Additional chain 2996 NI, additional stem 2999 (12") NI and/or 2997 (24") NI. May be installed with glass up or down. Sloped ceiling kit included.
B	3497	NI	(1) 100W (M)	4.5	14	46	68	36	Ⓢ (23-30W CFL) Additional chain 2996 NI, additional stem 2999 (12") NI and/or 2997 (24") NI. Height includes one 6" stem. Sloped ceiling kit included.
C	1896	NI	(5) 100W (M)	24	16.5	55	61	36	Ⓢ (23-30W CFL) Additional chain 2996 NI, additional stem 2999 (12") NI and/or 2997 (24") NI. Sloped ceiling kit included. May be installed glass up or down.
D	1897	NI	(9) 100W (M)	30	28.25	67	95	36	Ⓢ (23-30W CFL) Additional chain 2996 NI, additional stem 2999 (12") NI and/or 2997 (24") NI. Sloped ceiling kit included.
E	3299	NI	(4) 150W (M)	25.75	26.25	65	91	36	Ⓢ (23-30W CFL) Additional chain 2996 NI, additional stem 2999 (12") NI and/or 2997 (24") NI. Sloped ceiling kit included.

Measurements shown in inches.

Satin Etched
White GlassShown as
Semi Flush - 13.5" H.**CONVERTIBLE**Create two distinct lighting options
with one fixture: Semi Flush or
Inverted Pendant.**H** | 3797 NIShown as
Inverted Pendant - 14.5" H.**F** | 5096 NI
Wall Sconce**G** | 8043 NI
Flush Mount**J** | 3898 NI
Linear Chandelier**MATCHING
BATH**See matching
bath fixtures
on page 495.**MATCHING
MIRROR****41096 NI**
See page 412 or
kichler.com.**EILEEN™**

	ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	L	EXTRA WIRE	CHAIN/ STEM	EXT.	HCWO	NOTES
F	5096	NI	(1) 100W (M)	4.5	10.75	---	---	---	---	7	5.75	Ⓢ (18-25W CFL) May be installed with glass up or down.
G	8043	NI	(1) 100W (M)	5	6.25	---	---	---	---	---	---	Ⓢ (23-30W CFL)
H	3797	NI	(3) 100W (M)	17.25	14.5	53	---	21	36	---	---	Ⓢ (23-30W CFL) Additional chain 2996 NI.
J	3898	NI	(6) 100W (M)	16.25	18.5	57	30	95	36	---	---	Ⓢ (23-30W CFL) Additional chain 2996 NI, additional stem 2999 (12") NI and/or 2997 (24") NI. May be installed with glass up or down. Sloped ceiling kit included.

Measurements shown in inches.

EILEEN™

OLDE BRONZE® FINISH WITH
UMBER ETCHED GLASS



A | 1894 OZ
Mini Chandelier



B | 3497 OZ
Mini Pendant



C | 1896 OZ
Chandelier



D | 1897 OZ
Chandelier



E | 3299 OZ
Inverted Pendant

EILEEN™

ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/STEM	NOTES	
A	1894	OZ	(3) 100W (M)	18.5	13.75	52	63	36	Ⓜ (23-30W CFL) Additional chain 2996 OZ, additional stem 2999 (12") OZ. May be installed with glass up or down. Sloped ceiling kit included.
B	3497	OZ	(1) 100W (M)	4.5	14	46	68	36	Ⓜ (23-30W CFL) Additional chain 2996 OZ, additional stem 2999 (12") OZ. Height includes one 6" stem. Sloped ceiling kit included.
C	1896	OZ	(5) 100W (M)	24	16.5	55	61	36	Ⓜ (23-30W CFL) Additional chain 2996 OZ, additional stem 2999 (12") OZ. Sloped ceiling kit included. May be installed glass up or down.
D	1897	OZ	(9) 100W (M)	30	28.25	67	95	36	Ⓜ (23-30W CFL) Additional chain 2996 OZ, additional stem 2999 (12") OZ. Sloped ceiling kit included.
E	3299	OZ	(4) 150W (M)	25.75	26.25	65	91	36	Ⓜ (23-30W CFL) Additional chain 2996 OZ, additional stem 2999 (12") OZ. Sloped ceiling kit included.

Measurements shown in inches.



F | 5096 OZ
Wall Sconce



G | 8043 OZ
Flush Mount



J | 3898 OZ
Linear Chandelier



Shown as
Semi Flush - 13.5" H.

CONVERTIBLE

Create two distinct lighting options
with one fixture: Semi Flush or
Inverted Pendant.

H | 3797 OZ



Shown as
Inverted Pendant - 14.5" H.

MATCHING BATH

See matching
bath fixtures
on page 496.



MATCHING MIRROR

41096 OZ
See page 412 or
kichler.com.



EILEEN™

	ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	L	EXTRA WIRE	CHAIN/ STEM	EXT.	HCWO	NOTES
F	5096	OZ	(1) 100W (M)	4.5	10.75	---	---	---	---	7	5.75	Ⓜ (18-25W CFL) May be installed with glass up or down.
G	8043	OZ	(1) 100W (M)	5	6.25	---	---	---	---	---	---	Ⓜ (23-30W CFL)
H	3797	OZ	(3) 100W (M)	17.25	14.5	53	---	21	36	---	---	Ⓜ (23-30W CFL) Additional chain 2996 OZ.
J	3898	OZ	(6) 100W (M)	16.25	18.5	57	30	95	36	---	---	Ⓜ (23-30W CFL) Additional chain 2996 OZ, additional stem 2999 (12") OZ. May be installed with glass up or down. Sloped ceiling kit included.

Measurements shown in inches.

SHAILENE

BRUSHED NICKEL OR OLDE BRONZE® FINISH
WITH SATIN ETCHED GLASS



A | 43671 NI, OZ
Chandelier



B | 43672 NI, OZ
Chandelier

SHAILENE

ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/STEM	NOTES
A	43671 NI, OZ	(5) 100W (M)	23.5	18.25	57	57	36	(23-30W CFL) Additional chain 2996 NI, OZ, additional stem 2999 (12") NI, OZ and/or 2997 (24") NI. Sloped ceiling kit included.
B	43672 NI, OZ	(9) 100W (M)	26.25	26.5	65	94	36	(23-30W CFL) Additional chain 2996 NI, OZ, additional stem 2999 (12") NI, OZ and/or 2997 (24") NI. Sloped ceiling kit included.

Measurements shown in inches.



C | 45572 NI, OZ
Wall Sconce



D | 43675 NI, OZ
Semi Flush



E | 43674 NI, OZ
Mini Pendant



F | 43670 NI, OZ
Mini Chandelier

MATCHING BATH

See matching bath fixtures on pages 503-505.



SHAILENE

ITEM #	FINISH	INCAND. BULB	W	H	OVRLL. H	EXTRA WIRE	CHAIN/STEM	EXT.	HCWO	NOTES
C	45572 NI, OZ	(1) 100W (M)	5	8.25	---	---	---	6	4.75	D (23-30W CFL) May be installed with glass up or down.
D	43675 NI, OZ	(3) 100W (M)	14	10	---	---	---	---	---	E (23-30W CFL)
E	43674 NI, OZ	(1) 100W (M)	4.25	11	49	68	36	---	---	E (23-30W CFL) Additional chain 2996 NI, OZ, additional stem 2999 (12") NI, OZ and/or 2997 (24") NI. Sloped ceiling kit included.
F	43670 NI, OZ	(3) 100W (M)	17.5	15.25	54	60	36	---	---	E (23-30W CFL) Additional chain 2996 NI, OZ, additional stem 2999 (12") NI, OZ and/or 2997 (24") NI. Sloped ceiling kit included.

Measurements shown in inches.





Titus Pendant 43715 PN | Page 105 & Wall Sconce 43716 PN | Page 113

TITUS

POLISHED NICKEL FINISH WITH
BLACK MESH OUTER SHADE



A | 43715 PN
Chandelier/Pendant



B | 43712 PN
Oval Chandelier/Pendant




C | 43713 PN
Semi Flush



D | 43716 PN
Wall Sconce
ADA Compliant

TITUS

ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	L	STEM TILT	EXTRA WIRE	CHAIN/STEM	EXT.	HCWO	NOTES	
A	43715	PN	(8) 60W (C) B Type / G Type / 40W T Type	25	9.75	48	---	90°	73	36	---	---	Additional stem 2999 (12") PN.
B	43712	PN	(8) 60W (C) B Type / G Type / 40W T Type	17	9.75	48	37.25	90°	110	36	---	---	Additional stem 2999 (12") PN.
C	43713	PN	(4) 60W (C) B Type / G Type / 40W T Type	14.25	9.75	48	---	90°	73	36	---	---	Additional stem 2999 (12") PN.
D	43716	PN	(1) 60W (C) B Type / G Type / 40W T Type	6	12	---	---	---	---	---	4	6	

Measurements shown in inches. U.S. & Canada Patent Pending.

TITUS

POLISHED NICKEL FINISH WITH
BLACK MESH OUTER SHADE



A | 43712 PN
Oval Chandelier/Pendant
NOT TO SCALE



B | 43715 PN
Pendant



Shown as Pendant - 9.75" H.

CONVERTIBLE

Create two distinct lighting options with one fixture:
Pendant or Semi Flush.

D | 43713 PN

Black Mesh Shade



C | 43716 PN
Wall Sconce
ADA Compliant



Shown as Semi Flush - 10" H.

TITUS

ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	L	STEM TILT	EXTRA WIRE	CHAIN/STEM	EXT.	HCWO	NOTES
A	PN	(8) 60W (C) B Type / G Type / 40W T Type	17	9.75	48	37.25	90°	110	36	---	---	Additional stem 2999 (12") PN.
B	PN	(8) 60W (C) B Type / G Type / 40W T Type	25	9.75	48	---	90°	73	36	---	---	Additional stem 2999 (12") PN.
C	PN	(1) 60W (C) B Type / G Type / 40W T Type	6	12	---	---	---	---	---	4	6	Ⓧ Ⓡ
D	PN	(4) 60W (C) B Type / G Type / 40W T Type	14.25	9.75	48	---	90°	73	36	---	---	Additional stem 2999 (12") PN.

Measurements shown in inches. U.S. & Canada Patent Pending.

BERRA™

OLDE BRONZE® FINISH WITH
PARCHMENT GLASS



A | 43318 OZ
Linear Chandelier



B | 43320 OZ
Mini Pendant

BERRA™

ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	L	EXTRA WIRE	CHAIN/STEM	NOTES	
A	43318	OZ	(3) 100W (M)	3.5	15.5	54	34	72	36	(23-30W CFL) Additional chain 2996 OZ, additional stem 2999 (12") OZ. Sloped ceiling kit included.
B	43320	OZ	(1) 100W (M)	9.25	10.25	49	---	67	36	(23-30W CFL) Additional chain 2996 OZ, additional stem 2999 (12") OZ. Sloped ceiling kit included.

Measurements shown in inches. U.S. & Canada Patent Pending.

KAYDE™

OLDE BRONZE® FINISH
WITH CLEAR SEEDED GLASS



A | 42125 OZ
Mini Pendant



B | 42126 OZ
Wall Sconce



C | 42124 OZ
Linear Chandelier



VINTAGE
FILAMENT
BULB

SOLD SEPARATELY
60W Medium Base
4071 CLR

KAYDE™

ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	L	EXTRA WIRE	CHAIN/ STEM	EXT.	HCWO	NOTES	
A	42125	OZ	(1) 100W (M) A19 / 60W S21	4.5	9.75	48	---	67	36	---	---	Ⓜ (23-30W CFL) Additional chain 2996 OZ, additional stem 2999 (12") OZ. Sloped ceiling kit included.
B	42126	OZ	(1) 100W (M) A19 / 60W S21	4.75	12.25	---	---	---	---	5.75	8	Ⓜ (23-30W CFL)
C	42124	OZ	(5) 100W (M) A19 / 60W S21	3.5	15	53	40	98	36	---	---	Ⓜ (23-30W CFL) Additional chain 2996 OZ, additional stem 2999 (12") OZ. Sloped ceiling kit included.

Measurements shown in inches. U.S. & Canada Patent Pending.

ROCKLYN™

RAW STEEL FINISH WITH
NATURAL BRASS ACCENTS



A | 43718 RS
Pendant
NOT TO SCALE



VINTAGE
FILAMENT
BULB

SOLD SEPARATELY
60W Medium Base
4071 CLR



B | 43717 RS
Pendant



C | 43719 RS
Mini Pendant

ROCKLYN™

	ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/STEM	NOTES
A	43718	RS	(6) 100W (M)	22.75	36	74	70	36	Additional stem 2999 (12") RS. Sloped ceiling kit included.
B	43717	RS	(3) 100W (M)	17.75	36	74	70	36	Additional stem 2999 (12") RS. Sloped ceiling kit included.
C	43719	RS	(1) 100W (M)	8	9.25	113	---	---	Additional stem 2999 (12") RS.

Measurements shown in inches. U.S. & Canada Patent Pending.



Rumer™ Mini Chandelier 43587 NBR | Page 119

RUMER™

NATURAL BRASS WITH
DARK NATURAL BRASS ACCENTS

CONVERTIBLE

Create two distinct lighting options with one fixture:
Mini Pendant or Wall Sconce.

A | 43589 NBR



Shown as
Mini Pendant - 13.5" H.



Shown as
Wall Sconce - 12.75" H.

Dark Natural
Brass Accents

Adjustable Cord

Shown with Optional
Vintage Filament
Bulb 4071CLR



B | 43587 NBR
Mini Chandelier



VINTAGE
FILAMENT
BULB

SOLD SEPARATELY
60W Medium Base
4071 CLR

RUMER™

	ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/STEM	EXT.	HCWO	NOTES
A	43589	NBR	(1) 60W (M) S21 / 100W A19	5	13.5	46	50	---	5.25	2.5	Add. chain 2996 NBR, add. stem 2999 (12") NBR. Height does not incl. bulb. Sloped ceiling kit included. Height includes 6" stem.
B	43587	NBR	(4) 60W (M) S21 / 100W A19	17.5	21.25	60	74	36	---	---	Add. chain 2996 NBR, add. stem 2999 (12") NBR. Height does not incl. bulb. Sloped ceiling kit included.

Measurements shown in inches. U.S. & Canada Patent Pending.

BRAELYN™

OLDE BRONZE® FINISH WITH
CLEAR SEEDED GLASS



B | 43059 OZ
Linear Chandelier



Olde Bronze® Finish
with Highlights

Clear Seeded Glass

A | 43457 OZ
Linear Chandelier



VINTAGE
FILAMENT
BULB

SOLD SEPARATELY
60W Medium Base
4071 CLR

BRAELYN™

	ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	L	EXTRA WIRE	CHAIN/STEM	NOTES
A	43457	OZ	(8) 60W (M) A19 / S21	15	11.25	50	42	94	36	Ⓜ (13-15W CFL) Add. chain 2996 OZ, add. stem 2999 (12") OZ. Sloped ceiling kit incl.
B	43059	OZ	(6) 60W (M) A19 / S21	15	11.25	49	34	111	36	Ⓜ (13-15W CFL) Add. chain 2996 OZ, add. stem 2999 (12") OZ. Sloped ceiling kit incl.

Measurements shown in inches. U.S. & Canada Patent Pending.

Semi-Flush Mount
Option Available



C | 45457 OZ
Wall Sconce



D | 43060 OZ
Mini Pendant

**MATCHING
BATH**

See matching
bath fixtures
on page 431.



Shown as
Semi Flush - 11.25" H.

CONVERTIBLE

Create two distinct lighting
options with one fixture:
Semi Flush or Mini Chandelier.

F | 43057



Shown as
Mini Chandelier - 11" H.



E | 43058 OZ
Chandelier

BRAELYN™

	ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/STEM	EXT.	HCWO	NOTES
C	45457	OZ	(1) 60W (M) A19 / S21	5	9.5	---	---	---	5.75	6	Ⓢ (13-15W CFL)
D	43060	OZ	(1) 60W (M) A19 / S21	3.75	8.5	47	61	36	---	---	Ⓢ (13-15W CFL) Add. chain 2996 OZ, add. stem 2999 (12") OZ. Sloped ceiling kit incl.
E	43058	OZ	(5) 60W (M) A19 / S21	25	11.25	49	106	36	---	---	Ⓢ (13-15W CFL) Add. chain 2996 OZ, add. stem 4935 (12") OZ. Sloped ceiling kit incl.
F	43057	OZ	(3) 60W (M) A19 / S21	18	11	49	74	36	---	---	Ⓢ (13-15W CFL) Add. chain 2996 OZ, add. stem 2999 (12") OZ. Sloped ceiling kit incl.

Measurements shown in inches. U.S. & Canada Patent Pending.

INDUSTRIAL CAGE

WEATHERED ZINC FINISH

Cords Woven
as Shown or
Hung Straight



A | 43601 WZC
Pendant
NOT TO SCALE



B | 43603 WZC
Wall Sconce



C | 43602 WZC
Mini Pendant



D | 43600 WZC
Pendant



VINTAGE
FILAMENT
BULB

SOLD SEPARATELY
60W Medium Base
4071 CLR

INDUSTRIAL CAGE

	ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXT.	HCWO	NOTES
A	43601	WZC	(5) 100W (M) A19 / 60W S21	16.75	11.75	114	---	---	(23-30W CFL)
B	43603	WZC	(1) 100W (M) A19 / 60W S21	5.5	12.25	---	7.25	2.5	(23-30W CFL)
C	43602	WZC	(1) 100W (M) A19 / 60W S21	6.75	11	113	---	---	(23-30W CFL)
D	43600	WZC	(3) 100W (M) A19 / 60W S21	15.25	11.75	114	---	---	(23-30W CFL)

Measurements shown in inches. U.S. & Canada Patent Pending.

TINLEY

OLDE BRONZE® FINISH



A | 42854 OZ
Foyer Pendant



B | 42855 OZ
Foyer Pendant

TINLEY

	ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/STEM	NOTES
A	42854	OZ	(3) 60W (M) T Type	14	24.75	99	34	72	Additional chain 2996 OZ.
B	42855	OZ	(4) 60W (M) T Type	18	31.5	106	34	72	Additional chain 2996 OZ.

Measurements shown in inches. U.S. & Canada Patent Pending.

DARIA

OLDE BRONZE® FINISH



A | 43678 OZ
Mini Pendant



B | 43676 OZ
Pendant



VINTAGE
FILAMENT
BULB

SOLD SEPARATELY
40W Candelabra Base
5971 CLR



C | 43677 OZ
Linear Chandelier
NOT TO SCALE

DARIA

ITEM #	FINISH	INCAND. BULB	W	H	OVRLL. H	L	EXTRA WIRE	CHAIN/ STEM	NOTES	
A	43678	OZ	(2) 60W (C) B Type / G Type / 40W T Type	2.75	21.75	60	9.25	68	36	Additional chain 2996 OZ, additional stem 2999 (12") OZ. Sloped ceiling kit included.
B	43676	OZ	(6) 60W (C) B Type / G Type / 40W T Type	19.5	27	65	---	68	36	Additional chain 2996 OZ, additional stem 2999 (12") OZ. Sloped ceiling kit included.
C	43677	OZ	(8) 60W (C) B Type / G Type / 40W T Type	14.75	23	61	36	104	36	Additional chain 2996 OZ, additional stem 2999 (12") OZ. Sloped ceiling kit included.

Measurements shown in inches. U.S. & Canada Patent Pending.

LUCIEN™

OLDE BRONZE® FINISH



A | 42257 OZ
Chandelier Pendant
NOT TO SCALE



B | 42708 OZ
Chandelier



**VINTAGE
FILAMENT
BULB**

SOLD SEPARATELY
60W Medium Base
4071 CLR

LUCIEN™

	ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/ STEM	NOTES
A	42257	OZ	(9) 60W (M) S21 / A19 / G25	26	16.75	58	79	36	(13-15W CFL) Additional chain 2996 OZ, additional stem 4935 (12") OZ. Width includes bulbs. Sloped ceiling kit included.
B	42708	OZ	(6) 100W (M) A19 / 60W S21	25.25	28.75	103	10	72	(13-15W CFL) Additional chain 2996 OZ.

Measurements shown in inches. U.S. & Canada Patent Pending.

WESTINGTON™

OLDE BRONZE® FINISH WITH GOLD HIGHLIGHTS




A | 49588 OZ
Indoor/Outdoor Chandelier
NOT TO SCALE



B | 49585 OZ
Indoor/Outdoor Wall



C | 49586 OZ
Indoor/Outdoor Wall



D | 49587 OZ
Indoor/Outdoor Pendant



VINTAGE FILAMENT BULB

SOLD SEPARATELY
60W Medium Base
4071 CLR

WESTINGTON™

ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	L	EXTRA WIRE	CHAIN/ STEM	EXT.	HCWO	NOTES
A	0Z	(3) 100W (M) A19 / 60W S21	8	7.25	46	32	60	36	---	---	Ⓛ Additional chain 4927 OZ, additional stem 2999 (12") OZ. Sloped ceiling kit included.
B	0Z	(1) 100W (M) A19 / 60W S21	10	8.25	---	---	---	---	10.75	2.75	Ⓜ
C	0Z	(1) 100W (M) A19 / 60W S21	14	10	---	---	---	---	14.5	2.75	Ⓜ
D	0Z	(1) 100W (M) A19 / 60W S21	12	3.75	42	---	67	36	---	---	Ⓛ Additional chain 4927 OZ, additional stem 2999 (12") OZ. Sloped ceiling kit included.

Measurements shown in inches. U.S. & Canada Patent Pending.



Brinley™ Pendant 42877 NI | Page 132

BRINLEY™

BRUSHED NICKEL FINISH
WITH CLEAR GLASS

A | 42890 NI
Linear Chandelier



VINTAGE
FILAMENT
BULB

SOLD SEPARATELY
60W Medium Base
4071 CLR

BRINLEY™

	ITEM #	FINISH	INCAND. BULB	W	H	OVRL H	L	NOTES
A	42890	NI	(8) 100W (M) A19 / 60W S21	10.25	7.75	114	25.5	☑ (23-30W CFL)

Measurements shown in inches. U.S. & Canada Patent Pending.

BRINLEY™

BRUSHED NICKEL FINISH
WITH CLEAR GLASS



VINTAGE
FILAMENT
BULB

SOLD SEPARATELY
60W Medium Base
4071 CLR




A | 45576 NI
Wall Sconce



B | 42878 NI
Mini Pendant



C | 42891 NI
Flush Mount



Can be used with
or without included
cord ring to achieve
a different look



D | 42869 NI
Pendant



E | 42877 NI
Pendant

BRINLEY™

	ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXT.	HCWO	NOTES
A	45576	NI	(1) 100W (M) A19 / 60W S21	5	11.5	---	6.25	6	Ⓧ (23-30W CFL)
B	42878	NI	(1) 100W (M) A19 / 60W S21	4.75	7.75	113	---	---	Ⓧ (23-30W CFL)
C	42891	NI	(3) 75W (M) A19	11	8	---	---	---	Ⓧ (18-25W CFL)
D	42869	NI	(3) 100W (M) A19 / 60W S21	8.5	7.75	124	---	---	Ⓧ (23-30W CFL)
E	42877	NI	(6) 100W (M) A19 / 60W S21	12	7.75	113	---	---	Ⓧ (23-30W CFL)

Measurements shown in inches. U.S. & Canada Patent Pending.

BRINLEY™

OLDE BRONZE® FINISH
WITH CLEAR GLASS



A | 42890 OZ
Linear Chandelier



VINTAGE
FILAMENT
BULB

SOLD SEPARATELY
60W Medium Base
4071 CLR

BRINLEY™

ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	L	NOTES
A 42890	OZ	(8) 100W (M) A19 / 60W S21	10.25	7.75	114	25.5	☑ (23-30W CFL)

Measurements shown in inches. U.S. & Canada Patent Pending.

BRINLEY™

OLDE BRONZE® FINISH
WITH CLEAR GLASS



Mason Jar
Inspired Glass

A | 45576 OZ
Wall Sconce



B | 42891 OZ
Flush Mount




C | 42878 OZ
Mini Pendant


BRINLEY™

	ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXT.	HCWO	NOTES
A	45576	OZ	(1) 100W (M) A19 / 60W S21	5	11.5	---	6.25	6	Ⓧ (23-30W CFL)
B	42891	OZ	(3) 75W (M) A19 / 60W S21	11	8	---	---	---	Ⓧ (18-25W CFL)
C	42878	OZ	(1) 100W (M) A19 / 60W S21	4.75	7.75	113	---	---	Ⓧ (23-30W CFL)


Measurements shown in inches. U.S. & Canada Patent Pending.



Can be used with or without included cord ring to achieve a different look



D | 42869 OZ
Pendant



E | 42877 OZ
Pendant



**VINTAGE
FILAMENT
BULB**

SOLD SEPARATELY
60W Medium Base
4071 CLR

BRINLEY™

	ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	NOTES
D	42869	OZ	(3) 100W (M) A19 / 60W S21	8.5	7.75	124	☑ (23-30W CFL)
E	42877	OZ	(6) 100W (M) A19 / 60W S21	12	7.75	113	☑ (23-30W CFL)

Measurements shown in inches. U.S. & Canada Patent Pending.

SILBERNE™

NATURAL BRASS FINISH WITH
CLEAR SEEDED GLASS



A | 43741 NBR
Wall Sconce



B | 43740 NBR
Flush Mount



C | 43738 NBR
Pendant



D | 43737 NBR
Pendant



E | 43739 NBR
Pendant
NOT TO SCALE



VINTAGE
FILAMENT
BULB

SOLD SEPARATELY
60W Medium Base
4071 CLR

SILBERNE™

	ITEM #	FINISH	INCAND. BULB	W	H	OVRLL. H	EXTRA WIRE	CHAIN/ STEM	EXT.	HCWO	NOTES
A	43741	NBR	(1) 100W (M) A19 / 60W S21	10	10	---	---	---	11.5	6	D
B	43740	NBR	(3) 60W (M) A19 / 60W S21	18	10	---	---	---	---	---	
C	43738	NBR	(1) 100W (M) A19 / 60W S21	10	10	48	65	36	---	---	Add. chain 2996 NBR, add. stem 2999 (12") NBR. Sloped ceiling kit incl.
D	43737	NBR	(1) 100W (M) A19 / 60W S21	13	13.25	52	70	36	---	---	Add. chain 2996 NBR, add. stem 2999 (12") NBR. Sloped ceiling kit incl.
E	43739	NBR	(3) 100W (M) A19 / 60W S21	18	13	52	70	36	---	---	Add. chain 2996 NBR, add. stem 2999 (12") NBR. Sloped ceiling kit incl.

Measurements shown in inches. U.S. & Canada Patent Pending.

SILBERNE™

CLASSIC PEWTER FINISH WITH
CLEAR SEEDED GLASS

A | 43739 CLP
Pendant
NOT TO SCALE



B | 43741 CLP
Wall Sconce



C | 43740 CLP
Flush Mount



D | 43738 CLP
Pendant



E | 43737 CLP
Pendant



VINTAGE
FILAMENT
BULB

SOLD SEPARATELY
60W Medium Base
4071 CLR

SILBERNE™

	ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/ STEM	EXT.	HCWO	NOTES
A	43739	CLP	(3) 100W (M) A19 / 60W S21	18	13	52	70	36	---	---	Add. chain 2996 CLP, add. stem 2999 (12") CLP. Sloped ceiling kit incl.
B	43741	CLP	(1) 100W (M) A19 / 60W S21	10	10	---	---	---	11.5	6	D
C	43740	CLP	(3) 60W (M) A19 / 60W S21	18	10	---	---	---	---	---	
D	43738	CLP	(1) 100W (M) A19 / 60W S21	10	10	48	65	36	---	---	Add. chain 2996 CLP, add. stem 2999 (12") CLP. Sloped ceiling kit incl.
E	43737	CLP	(1) 100W (M) A19 / 60W S21	13	13.25	52	70	36	---	---	Add. chain 2996 CLP, add. stem 2999 (12") CLP. Sloped ceiling kit incl.

Measurements shown in inches. U.S. & Canada Patent Pending.

GRAND BANK™

AUBURN STAINED WOOD FINISH & DISTRESSED
BLACK METAL FINISH WITH CLEAR SEEDED GLASS



A | 43193 AUB
Chandelier
NOT TO SCALE



B | 43185 AUB
Chandelier



Auburn Stained Wood

C | 43190 AUB
Chandelier

GRAND BANK™

	ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	STEM TILT	EXTRA WIRE	CHAIN/STEM	NOTES
A	43193	AUB	(6) 60W (C)	25	22.5	61	---	74	36	Additional chain 2996 DBK, additional stem 2999 (12") DBK. Sloped ceiling kit included.
B	43185	AUB	(4) 60W (C)	20	21.5	60	90°	74	36	Additional stem 2999 (12") DBK.
C	43190	AUB	(8) 60W (C)	28	29.5	68	90°	107	36	Additional stem 2999 (12") DBK.


Measurements shown in inches. U.S. & Canada Patent Pending.

GRAND BANK™

AUBURN STAINED WOOD FINISH & DISTRESSED BLACK METAL FINISH WITH CLEAR SEEDED GLASS



A | 43191 AUB
Oval Chandelier



GRAND BANK™

	ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	L	STEM TILT	EXTRA WIRE	CHAIN/STEM	EXT.	HCWO	NOTES
A	43191	AUB	(8) 60W (C)	16	15.75	56	36	---	85	36	---	---	Additional stem 2999 (12") DBK, additional chain 2996 DBK. Sloped ceiling kit included.
B	43186	AUB	(5) 60W (C)	2.75	15.75	54	36	90°	94	36	---	---	Additional stem 2999 (12") DBK.
C	43189	AUB	(1) 60W (C)	9	9.75	48	---	90°	58	36	7.5	2.5	Additional stem 2999 (12") DBK.

Measurements shown in inches. U.S. & Canada Patent Pending.



B | 43186 AUB
Linear Chandelier



PENDALETTE®

Create three distinct lighting options with one fixture: Wall Sconce, Semi Flush, or Mini Pendant.

C | 43189 AUB

Shown as
Wall Sconce -
12.5" H.

Shown as
Mini Pendant -
9.75" H.


Shown as
Semi Flush - 12.25" H.



Colerne™ Linear Chandelier 43433 AUB | Page 144

COLERNE™

AUBURN STAINED WOOD FINISH
& DISTRESSED BLACK METAL FINISH
WITH CLEAR SEEDED GLASS



COLERNE™

ITEM #	FINISH	INCAND. BULB	W	H	OVRLL. H	L	EXTRA WIRE	CHAIN/STEM	NOTES
A 43491	AUB	(5) 100W (M) A19 / 60W S21 & (3) 50W (GU10)	10.75	21	59	46.5	78	36	(23-30W CFL) Additional chain 4901 DBK, additional stem 4935 (12") DBK. Sloped ceiling kit included.

Measurements shown in inches. U.S. & Canada Patent Pending.

COLERNE™

AUBURN STAINED WOOD FINISH
& DISTRESSED BLACK METAL FINISH
WITH CLEAR SEEDED GLASS



Downlight

A | 43433 AUB
Linear Chandelier

Features
3-Way Switch



VINTAGE
FILAMENT
BULB

SOLD SEPARATELY
60W Medium Base
4071 CLR



B | 43436 AUB
Wall Sconce



C | 43435 AUB
Pendant

COLERNE™

	ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	L	EXTRA WIRE	CHAIN/STEM	EXT.	HCWO	NOTES
A	43433	AUB	(3) 100W (M) A19 / 60W S21 & (3) 50W (GU10)	10.5	16.75	55	35.75	52	36	---	---	Ⓜ (23-30W CFL) Additional chain 4901 DBK, additional stem 4935 (12") DBK. Sloped ceiling kit included.
B	43436	AUB	(1) 100W (M) A19	8.75	14.75	---	---	---	---	9.5	7.25	Ⓜ (23-30W CFL)
C	43435	AUB	(1) 100W (M) A19 & (1) 50W (GU10)	10.5	16.5	55	---	46	36	---	---	Ⓜ (23-30W CFL) Additional chain 2996 DBK, additional stem 4935 (12") DBK. Sloped ceiling kit included.

Measurements shown in inches. U.S. & Canada Patent Pending.

CLAGUE™

DISTRESSED BLACK FINISH WITH
AUBURN STAINED WOOD FINISH CENTER COLUMN



A | 43419 DBK
Chandelier
NOT TO SCALE



VINTAGE FILAMENT BULB

SOLD SEPARATELY
40W Candelabra Base
5971 CLR



B | 43420 DBK
Large Foyer Pendant

CLAGUE™

	ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/ STEM	NOTES
A	43419	DBK	(5) 60W (C)	26.5	23.25	61	89	36	Additional chain 2996 DBK, additional stem 2999 (12") DBK. Sloped ceiling kit included.
B	43420	DBK	(4) 60W (C)	18	23	61	86	36	Additional chain 2996 DBK, additional stem 2999 (12") DBK. Sloped ceiling kit included.


Measurements shown in inches. U.S. & Canada Patent Pending.



Cahoon Wall Sconce 43777 AVI | Page 151 & Linear Chandelier 43774 AVI | Page 151

CAHOON™

ANVIL IRON & DISTRESSED ANTIQUE GRAY FINISH
WITH BEIGE LINEN SHADE



A | 43774 AVI
Linear Chandelier



B | 43776 AVI
Pendant



C | 43775 AVI
Pendant/Semi Flush



D | 43777 AVI
Wall Sconce

CAHOON™

	ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	L	EXTRA WIRE	CHAIN/STEM	EXT.	HCWO	NOTES
A	43774	AVI	(3) 100W (M)	13.5	13	51	37.25	102	36	---	---	☑ (23-30W CFL) Additional chain 2996 AVI, additional stem 4935 (12") AVI. Sloped ceiling kit included.
B	43776	AVI	(4) 100W (M)	25.75	12.75	52	---	68	36	---	---	☑ (23-30W CFL) Additional chain 2996 AVI, additional stem 4935 (12") AVI. Sloped ceiling kit included.
C	43775	AVI	(1) 100W (M)	16.25	12	51	---	72	36	---	---	☑ (23-30W CFL) Additional chain 2996 AVI, additional stem 4935 (12") AVI. Sloped ceiling kit included.
D	43777	AVI	(2) 60W (C) ✓	7.5	15	---	---	---	---	5.5	7.75	

Measurements shown in inches. U.S. & Canada Patent Pending.

CAHOON™

ANVIL IRON & DISTRESSED ANTIQUE GRAY FINISH
WITH BEIGE LINEN SHADE



A | 43774 AVI
Linear Chandelier



Shown as
Pendant - 50.5" H.

CONVERTIBLE

Create two distinct lighting
options with one fixture:
Pendant or Semi Flush.

B | 43775 AVI



Shown as
Semi Flush - 12.5" H.



C | 43776 AVI
Pendant

Satin Etched
Glass Diffuser



D | 43777 AVI
Wall Sconce

CAHOON™

ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	L	EXTRA WIRE	CHAIN/ STEM	EXT.	HCWO	NOTES	
A	43774	AVI	(3) 100W (M)	13.5	13	51	37.25	102	36	---	---	☑ (23-30W CFL) Additional chain 2996 AVI, additional stem 4935 (12") AVI. Sloped ceiling kit included.
B	43775	AVI	(1) 100W (M)	16.25	12	51	---	72	36	---	---	☑ (23-30W CFL) Additional chain 2996 AVI, additional stem 4935 (12") AVI. Sloped ceiling kit included.
C	43776	AVI	(4) 100W (M)	25.75	12.75	52	---	68	36	---	---	☑ (23-30W CFL) Additional chain 2996 AVI, additional stem 4935 (12") AVI. Sloped ceiling kit included.
D	43777	AVI	(2) 60W (C) ✓	7.5	15	---	---	---	---	5.5	7.75	

Measurements shown in inches. U.S. & Canada Patent Pending.



Evan™ Chandelier 43324 DAG | Page 154

EVAN™

DISTRESSED ANTIQUE GRAY FINISH ON
WOOD WITH ANVIL IRON DETAILING



A | 43327 DAG
Chandelier

EVAN™

ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/ STEM	NOTES
A 43327	DAG	(6) 60W (C) B Type / 40W T Type	28.5	37.5	112	48	72	Additional chain 2996 AVI.

Measurements shown in inches. U.S. & Canada Patent Pending.

EVAN™

DISTRESSED ANTIQUE GRAY FINISH ON
WOOD WITH ANVIL IRON DETAILING



A | 43324 DAG
Chandelier




B | 43322 DAG
Chandelier



VINTAGE
FILAMENT
BULB

SOLD SEPARATELY
40W Candelabra Base
5971 CLR



EVAN™

	ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	STEM TILT	EXTRA WIRE	CHAIN/ STEM	EXT.	HCWO	NOTES
A	43324	DAG	(5) 60W (C) B Type / 40W T Type	20	30	104	---	20	72	---	---	Additional chain 2996 AVI.
B	43322	DAG	(5) 60W (C) B Type / 40W T Type	24	27	101	---	18	72	---	---	Additional chain 2996 AVI.
C	43328	DAG	(2) 60W (C)	13	13.75	52	90°	65	36	7.5	2.5	Additional stem 2999 (12") AVI.

Measurements shown in inches. U.S. & Canada Patent Pending.

AHRENDALE™

ANVIL IRON FINISH & DISTRESSED
ANTIQUÉ GRAY ON WOOD WITH
VETRO MICA GLASS



A | 43582 AVI
Chandelier
NOT TO SCALE



B | 43584 AVI
Mini Pendant



C | 43586 AVI
Wall Sconce



D | 43581 AVI

CONVERTIBLE

Create two distinct lighting options with one fixture:
Semi Flush or Mini Chandelier.



Shown as
Semi Flush - 15.75" H.



Shown as
Mini Chandelier - 16.75" H.

AHRENDALE™

ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/STEM	EXT.	HCWO	NOTES
A	AVI	(4) 100W (M) A19 / 60W S21	24	30	104	47	72	---	---	☑ (23-30W CFL) Additional chain 2996 AVI.
B	AVI	(1) 100W (M) A19 / 60W S21	6	13	51	61	36	---	---	☑ (23-30W CFL) Additional chain 2996 AVI. Additional stem 2999 (12") AVI. Sloped ceiling kit included.
C	AVI	(1) 60W (C) B Type / 40W T Type	7.5	10	---	---	---	3.75	4	ⓓ
D	AVI	(3) 100W (M) A19 / 60W S21	17.75	16.75	91	25	72	---	---	☑ (23-30W CFL) Additional chain 2996 AVI.

Measurements shown in inches. U.S. & Canada Patent Pending.



Kimblewick™ Chandelier 43617 WZC | Page 161

KIMBLEWICK™

WEATHERED ZINC FINISH WITH
DISTRESSED ANTIQUE WHITE FINISH &
PARCHMENT GLASS ACCENTS



A | 43618 WZC
Chandelier



B | 43617 WZC
Chandelier



C | 43615 WZC
Chandelier



D | 43616 WZC
Mini Chandelier

KIMBLEWICK™

ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/STEM	NOTES
A	43618 WZC	(9) 60W (C) B Type / 40W T Type	27	32.25	107	51	72	Additional chain 2996 WZC.
B	43617 WZC	(6) 60W (C) B Type / 40W T Type	26	27.75	102	54	72	Additional chain 2996 WZC.
C	43615 WZC	(4) 60W (C) B Type / 40W T Type	18	20.25	95	23	72	Additional chain 2996 WZC.
D	43616 WZC	(3) 60W (C) B Type / 40W T Type	12.25	15.5	91	26	72	Additional chain 2996 WZC.

Measurements shown in inches. U.S. & Canada Patent Pending.

KIMBLEWICK™

WEATHERED ZINC FINISH WITH
DISTRESSED ANTIQUE WHITE FINISH &
PARCHMENT GLASS ACCENTS



A | 43618 WZC
Chandelier
NOT TO SCALE



B | 43617 WZC
Chandelier



C | 43616 WZC
Mini Chandelier



D | 43615 WZC
Chandelier

KIMBLEWICK™

ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/STEM	NOTES	
A	43618	WZC	(9) 60W (C) B Type / 40W T Type	27	32.25	107	51	72	Additional chain 2996 WZC.
B	43617	WZC	(6) 60W (C) B Type / 40W T Type	26	27.75	102	54	72	Additional chain 2996 WZC.
C	43616	WZC	(3) 60W (C) B Type / 40W T Type	12.25	15.5	91	26	72	Additional chain 2996 WZC.
D	43615	WZC	(4) 60W (C) B Type / 40W T Type	18	20.25	95	23	72	Additional chain 2996 WZC.

Measurements shown in inches. U.S. & Canada Patent Pending.

HAYMAN BAY™

DISTRESSED ANTIQUE WHITE FINISH



B | 43256 DAW
Chandelier



A | 43265 DAW
Chandelier



C | 43258 DAW
Indoor Pendant



D | 43259 DAW
Indoor Pendant



E | 43255 DAW
Foyer Chandelier



F | 43257 DAW
Chandelier

HAYMAN BAY™

	ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/STEM	NOTES
A	43265	DAW	(8) 60W (C)	32	32.5	107	32	72	Additional Chain 2996 DAW.
B	43256	DAW	(5) 60W (C)	28	29.75	104	33	72	Additional chain 2996 DAW.
C	43258	DAW	(2) 60W (C)	8.5	18	92	23	72	Ⓧ Additional chain 2996 DAW.
D	43259	DAW	(4) 60W (C)	15	29.75	104	10	72	Ⓧ Additional chain 2996 DAW.
E	43255	DAW	(4) 60W (C)	16.25	29.75	104	15	72	Additional chain 2996 DAW.
F	43257	DAW	(6) 60W (C)	27	29.75	104	51	72	Additional chain 2996 DAW.

Measurements shown in inches. U.S. & Canada Patent Pending.



Organique™ Chandelier 42888 OZ | Page 166

ORGANIQUE™

OLDE BRONZE® FINISH



A | 42888 OZ
Chandelier



B | 42887 OZ
Chandelier



C | 42886 OZ
Mini Chandelier

ORGANIQUE™

	ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/STEM	NOTES
A	42888	OZ	(6) 60W (C)	30	20.75	95	58	72	Additional chain 2996 OZ.
B	42887	OZ	(5) 60W (C)	24	16	90	26	72	Additional chain 2996 OZ.
C	42886	OZ	(3) 60W (C)	18	14	88	28	72	Additional chain 2996 OZ.

Measurements shown in inches. U.S. & Canada Patent Pending.

ORGANIQUE™

OLDE BRONZE® FINISH



A | 42888 OZ
Chandelier
NOT TO SCALE



VINTAGE
FILAMENT
BULB

SOLD SEPARATELY
40W Candelabra Base
5971 CLR



B | 42887 OZ
Chandelier



C | 42886 OZ
Mini Chandelier

ORGANIQUE™

	ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/STEM	NOTES
A	42888	OZ	(6) 60W (C)	30	20.75	95	58	72	Additional chain 2996 OZ.
B	42887	OZ	(5) 60W (C)	24	16	90	26	72	Additional chain 2996 OZ.
C	42886	OZ	(3) 60W (C)	18	14	88	28	72	Additional chain 2996 OZ.

Measurements shown in inches. U.S. & Canada Patent Pending.

KEARN™

OLDE BRONZE® FINISH WITH
WRAPPED ROPE ACCENTS

Wrapped Rope Accents



A | 43424 OZ
Chandelier



Shown with
Optional Mica
Shade 4121

A | 43424 OZ
Chandelier

OPTIONAL SHADES



5" x 4.25" - Mica Fabric Shade
4121



4.25" x 6.5" - Clear Seeded Glass
4122

KEARN™

	ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	L	EXTRA WIRE	CHAIN/ STEM	NOTES
A	43424	OZ	(10) 60W (C)	33.75	39.25	114	---	38	72	Additional chain 4901 OZ.
B	43423	OZ	(6) 60W (C)	25	26	99	---	6	72	Additional chain 2996 OZ.
C	43422	OZ	(8) 60W (C)	23.75	28.25	103	37.75	37	72	Additional chain 2996 OZ.


Measurements shown in inches. U.S. & Canada Patent Pending.



B | 43423 OZ
Chandelier




C | 43422 OZ
Oval Chandelier



B | 43423 OZ
Chandelier



C | 43422 OZ
Oval Chandelier



TAULBEE™

WEATHERED ZINC METAL FINISH WITH
WEATHERED GRAY WOOD FINISH



A | 43826 WZC
Chandelier
NOT TO SCALE



VINTAGE FILAMENT BULB

SOLD SEPARATELY
40W Candelabra Base
5971 CLR



B | 43823 WZC
Chandelier



C | 43825 WZC
Wall Sconce



D | 43824 WZC
Oval Chandelier/Pendant

TAULBEE™

	ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	L	EXTRA WIRE	CHAIN/STEM	EXT.	HCWO	NOTES
A	43826	WZC	(15) 60W (C)	44	38.75	112	---	52	72	---	---	Additional chain 4901 (12") WZC.
B	43823	WZC	(6) 60W (C)	28.5	26	100	---	52	72	---	---	Additional chain 2996 (12") WZC.
C	43825	WZC	(1) 60W (C)	4.75	18	---	---	---	---	7.5	5.5	
D	43824	WZC	(6) 60W (C)	18	28.25	103	36	48	72	---	---	Additional chain 2996 (12") WZC.

Measurements shown in inches.



Caldella™ Chandelier 43772 AGZ | Page 174

CALDELLA™

AGED BRONZE FINISH WITH
FLEUR-DE-LIS DETAILS



A | 43779 AGZ
Grand Chandelier

CALDELLA™

ITEM #	FINISH	INCAND. BULB	W	H	OVRLL. H	EXTRA WIRE	CHAIN/STEM	NOTES
A 43779	AGZ	(12) 60W (C)	49	49.75	124	72	72	Additional chain 2996 (12") AGZ.

Measurements shown in inches. U.S. & Canada Patent Pending.

CALDELLA™

AGED BRONZE FINISH WITH
FLEUR-DE-LIS DETAILS



A | 43772 AGZ
Chandelier
NOT TO SCALE



B | 43771 AGZ
Chandelier



C | 43773 AGZ
Wall Sconce



D | 43770 AGZ
Mini Chandelier

CALDELLA™

	ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/STEM	EXT.	HCWO	NOTES
A	43772	AGZ	(8) 60W (C) B Type / G Type / 40W T Type	33	37	111	29	72	---	---	Additional chain 2996 AGZ.
B	43771	AGZ	(6) 60W (C) B Type / G Type / 40W T Type	26.75	31.25	106	38	72	---	---	Additional chain 2996 AGZ.
C	43773	AGZ	(1) 60W (C) B Type / G Type / 40W T Type	5	12	---	---	---	8	10.75	ⓓ Height does not include bulb.
D	43770	AGZ	(3) 60W (C) B Type / G Type / 40W T Type	19	22	96	14	72	---	---	Additional chain 2996 AGZ.

Measurements shown in inches. U.S. & Canada Patent Pending.

CATERHAM™

OLDE BRONZE® FINISH WITH
SATIN ETCHED CASED OPAL GLASS



A | 49638 OZ
Indoor/Outdoor Chandelier
NOT TO SCALE



Satin Etched
Cased Opal Glass

B | 49640 OZ
Indoor/Outdoor Mini Pendant



C | 49642 OZ
Indoor/Outdoor Wall Sconce



D | 49643 OZ
Indoor/Outdoor Wall Sconce



E | 49644 OZ
Indoor/Outdoor Wall Sconce



F | 49641 OZ
Indoor/Outdoor Semi Flush

Satin Etched
White Glass

CATERHAM™

	ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/STEM	EXT.	HCWO	NOTES
A	49638	OZ	(4) 100W (M)	21	12.75	51	67	36	---	---	D OD (23-30W CFL) Additional chain 4927 OZ, additional stem 2999 (12") OZ. Sloped ceiling kit included.
B	49640	OZ	(1) 100W (M)	6.5	16	48	58	36	---	---	D OD (23-30W CFL) Additional chain 4927 OZ, additional stem 2999 (12") OZ. Height includes one 6" stem. Sloped ceiling kit included.
C	49642	OZ	(1) 100W (M)	6.5	11.75	---	---	---	7.5	4	W OD (23-30W CFL)
D	49643	OZ	(1) 100W (M)	8	14.75	---	---	---	9	4	W OD (23-30W CFL)
E	49644	OZ	(1) 150W (M)	10	17.5	---	---	---	10.75	4.5	W OD (30-52W CFL)
F	49641	OZ	(3) 100W (M)	14.75	8.75	---	---	---	---	---	D OD (23-30W CFL)

Measurements shown in inches. U.S. & Canada Patent Pending.

ALAMEDA™

CANYON VIEW™ FINISH OVER
SOLID BRASS WITH HONEY
OPALESCENT ART GLASS PANELS



A | 49091 CV
Indoor/Outdoor Chandelier
NOT TO SCALE



B | 9649 CV
Indoor/Outdoor Wall Sconce



C | 9652 CV
Indoor/Outdoor Wall Sconce



D | 9651 CV
Indoor/Outdoor Wall Sconce



E | 9148 CV
Indoor/Outdoor Wall Sconce



F | 9825 CV
Indoor/Outdoor Flush Mount



G | 9849 CV
Indoor/Outdoor Pendant

ALAMEDA™

ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/STEM	EXT.	HCWO	NOTES	
A	49091	CV	(4) 100W (M)	25	17	55	59	36	---	---	Ⓛ Add. chain 4927 CV, add. stem 2999 (12") CV. Sloped ceiling kit incl.
B	9649	CV	(1) 75W (M) ✓	5	7	---	---	---	5.75	4	Ⓜ Ⓜ (OD 18-25W CFL)
C	9652	CV	(1) 150W (M)	9	14.25	---	---	---	10.45	3.5	Ⓜ Ⓜ (OD 23-30W CFL)
D	9651	CV	(1) 100W (M)	7	11.5	---	---	---	8.5	3	Ⓜ Ⓜ (OD 23-30W CFL) Dark sky compliant with panel inserts 4812 WH.
E	9148	CV	(1) 150W (M)	7	15	---	---	---	8.5	3	Ⓜ Ⓜ (OD 18-25W CFL)
F	9825	CV	(2) 75W (M) ❖	11.5	6.25	---	---	---	---	---	Ⓛ Ⓜ (OD 18-25W CFL)
G	9849	CV	(1) 100W (M)	7	11	86	28	72	---	---	Ⓛ Ⓜ (OD 23-30W CFL) Dark sky compliant with panel inserts 4814WH. Add. chain 4927 CV.

Measurements shown in inches.

GRAYSON

NATURAL BRASS FINISH



A | 43908 NBR
Chandelier
NOT TO SCALE



B | 43907 NBR
Chandelier






C | 43909 NBR
Flush Mount



D | 43910 NBR
Wall Sconce

GRAYSON

	ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/STEM	EXT.	HWCO	NOTES
A	43908	NBR	(15) 60W (C)	36	24.75	99	55	72	---	---	Additional chain 2996 (12") NBR.
B	43907	NBR	(8) 60W (C)	28	18.25	92	61	72	---	---	Additional chain 2996 (12") NBR.
C	43909	NBR	(2) 75W (M) A19 	17	5	---	---	---	---	---	 (23-30W CFL)
D	43910	NBR	(1) 60W (C)	4.5	12.5	---	---	---	6	6.25	

Measurements shown in inches. U.S. & Canada Patent Pending.

GRAYSON

CLASSIC PEWTER FINISH



A | 43908 CLP
Chandelier
NOT TO SCALE



B | 43907 CLP
Chandelier






C | 43909 CLP
Flush Mount



D | 43910 CLP
Wall Sconce

GRAYSON

	ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/STEM			NOTES
A	43908	CLP	(15) 60W (C)	36	24.75	99	55	72	---	---	Additional chain 2996 (12") CLP.
B	43907	CLP	(8) 60W (C)	28	18.25	92	61	72	---	---	Additional chain 2996 (12") CLP.
C	43909	CLP	(2) 75W (M) A19 	17	5	---	---	---	---	---	 (23-30W CLF)
D	43910	CLP	(1) 60W (C)	4.5	12.5	---	---	---	6	6.25	

Measurements shown in inches. U.S. & Canada Patent Pending.



Signata™ Chandelier 43701 NBR | Page 188 & Wall Sconce 45701 NBR | Page 188

SIGNATA™

NATURAL BRASS OR CLASSIC PEWTER FINISH WITH
CLEAR CURVED GLASS PANELS



A | 43700 NBR
Mini Chandelier



B | 43705 NBR
Mini Pendant



C | 45701 NBR
Wall Sconce



D | 43704 NBR
Chandelier



E | 43703 NBR
Linear Chandelier



F | 43702 NBR
Chandelier



G | 43701 NBR
Chandelier

SIGNATA™

ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	STEM TILT	L	EXTRA WIRE	CHAIN/STEM	EXT.	HCWO	NOTES	
A	43700	NBR	(3) 60W (C) B Type / 40W T Type	18	18	92	---	---	20	72	---	---	Add. chain 2996 NBR.
B	43705	NBR	(1) 60W (C) B Type / 40W T Type	4.5	12.25	51	90°	5	58	36	---	---	Add. stem 2999 (12") NBR.
C	45701	NBR	(1) 60W (C) B Type / 40W T Type	5.75	8	---	---	---	---	4	4.25	ⓓ Ⓞ	
D	43704	NBR	(9) 60W (C) B Type / 40W T Type	32.75	25.5	100	---	---	51	72	---	---	Add. chain 2996 NBR.
E	43703	NBR	(8) 60W (C) B Type / 40W T Type	18	22	60	---	38	87	36	---	---	Add. chain 2996 NBR, add. stem 2999 (12") NBR. Sloped ceiling kit incl.
F	43702	NBR	(8) 60W (C) B Type / 40W T Type	30	24.5	99	---	---	46	72	---	---	Add. chain 2996 NBR.
G	43701	NBR	(6) 60W (C) B Type / 40W T Type	26	21	95	---	---	15	72	---	---	Add. chain 2996 NBR.

Measurements shown in inches. U.S. & Canada Patent Pending.

SIGNATA™

NATURAL BRASS FINISH WITH
CLEAR CURVED GLASS PANELS

MATCHING BATH

See matching
bath fixtures
on page 434.



Shown with
5971 CLR Bulb



A | 43704 NBR
Chandelier
NOT TO SCALE



VINTAGE FILAMENT BULB

SOLD SEPARATELY
40W Candelabra Base
5971 CLR



B | 43702 NBR
Chandelier



C | 43703 NBR
Linear Chandelier

SIGNATA™

	ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	L	EXTRA WIRE	CHAIN/ STEM	NOTES
A	43704	NBR	(9) 60W (C) B Type / 40W T Type	32.75	25.5	100	---	51	72	Additional chain 2996 NBR.
B	43702	NBR	(8) 60W (C) B Type / 40W T Type	30	24.5	99	---	46	72	Additional chain 2996 NBR.
C	43703	NBR	(8) 60W (C) B Type / 40W T Type	18	22	60	38	87	36	Add. chain 2996 NBR, add. stem 2999 (12") NBR. Sloped ceiling kit incl.

Measurements shown in inches. U.S. & Canada Patent Pending.

SIGNATA™

NATURAL BRASS FINISH WITH
CLEAR CURVED GLASS PANELS



A | 45701 NBR
Wall Sconce
ADA Compliant



B | 43705 NBR
Mini Pendant



C | 43700 NBR
Mini Chandelier



D | 43701 NBR
Chandelier

SIGNATA™

ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	STEM TILT	L	EXTRA WIRE	CHAIN/STEM	EXT.	HCWO	NOTES
A	45701	NBR	(1) 60W (C) B Type / 40W T Type	5.75	8	---	---	---	---	4	4.25	Ⓟ Ⓡ
B	43705	NBR	(1) 60W (C) B Type / 40W T Type	4.5	12.25	51	90°	5	58	36	---	Additional stem 2999 (12") NBR.
C	43700	NBR	(3) 60W (C) B Type / 40W T Type	18	18	92	---	20	72	---	---	Additional chain 2996 NBR.
D	43701	NBR	(6) 60W (C) B Type / 40W T Type	26	21	95	---	15	72	---	---	Additional chain 2996 NBR.

Measurements shown in inches. U.S. & Canada Patent Pending.

MATCHING BATH

See matching bath fixtures on page 435.



SIGNATA™

CLASSIC PEWTER FINISH WITH CLEAR CURVED GLASS PANELS

Shown with 5971 CLR Bulb



A | 43704 CLP Chandelier NOT TO SCALE



VINTAGE FILAMENT BULB

SOLD SEPARATELY
40W Candelabra Base
5971 CLR

SIGNATA™

ITEM #	FINISH	INCAND. BULB	W	H	OVRLL. H	EXTRA WIRE	CHAIN/STEM	NOTES
A 43704	CLP	(9) 60W (C) B Type / 40W T Type	32.75	25.5	100	51	72	Additional chain 2996 CLP

Measurements shown in inches. U.S. & Canada Patent Pending.

SIGNATA™

CLASSIC PEWTER FINISH WITH
CLEAR CURVED GLASS PANELS



A | 43702 CLP
Chandelier



B | 43703 CLP
Linear Chandelier



C | 45701 CLP
Wall Sconce
ADA Compliant



D | 43705 CLP
Mini Pendant




E | 43700 CLP
Mini Chandelier



F | 43701 CLP
Chandelier

SIGNATA™

	ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	STEM TILT	L	EXTRA WIRE	CHAIN/ STEM	EXT.	HCWO	NOTES
A	43702	CLP	(8) 60W (C) B Type / 40W T Type	30	24.5	100	---	---	46	72	---	---	Add. chain 2996 CLP.
B	43703	CLP	(8) 60W (C) B Type / 40W T Type	18	22	60	---	38	87	36	---	---	Add. chain 2996 CLP, add. stem 2999 (12") CLP. Sloped ceiling kit incl.
C	45701	CLP	(1) 60W (C) B Type / 40W T Type	5.75	8	---	---	---	---	---	4	4.25	
D	43705	CLP	(1) 60W (C) B Type / 40W T Type	4.5	12.25	51	90°	5	58	36	---	---	Add. stem 2999 (12") CLP.
E	43700	CLP	(3) 60W (C) B Type / 40W T Type	18	18	92	---	---	20	72	---	---	Add. chain 2996 CLP.
F	43701	CLP	(6) 60W (C) B Type / 40W T Type	26	21	95	---	---	15	72	---	---	Add. chain 2996 CLP.

Measurements shown in inches. U.S. & Canada Patent Pending.



Emory Pendant 43706 CLP | Page 195 & Mona Wall Sconce 43376 CLP | Page 396

EMORY

CLASSIC PEWTER FINISH WITH CLEAR GLASS
OR OFF WHITE FABRIC SHADE OR
OLDE BRONZE® FINISH WITH CLEAR GLASS
OR OFF WHITE FABRIC SHADE



A | 43710 CLP
Wall Sconce



B | 43709 CLP
Foyer Pendant



C | 43706 CLP
Pendant



D | 43707 CLP
Chandelier

EMORY

	ITEM #	FINISH	INCAND. BULB	W	H	OVRLL. H	EXTRA WIRE	CHAIN/STEM	EXT.	HCWO	NOTES
A	43710	CLP	(2) 60W (C)	8.5	15.5	---	---	---	5.25	9	ⓓ
B	43709	CLP	(4) 60W (C)	15	27.5	68	46	36	---	---	Additional chain 2996 CLP.
C	43706	CLP	(3) 100W (M)	18	10.25	49	67	36	---	---	ⓓ (23-30W CFL) Additional chain 2996 CLP.
D	43707	CLP	(4) 100W (M)	24	11.5	50	66	36	---	---	Additional chain 2996 CLP.

Measurements shown in inches. U.S. & Canada Patent Pending.

EMORY

CLASSIC PEWTER FINISH WITH CLEAR GLASS
OR OFF WHITE FABRIC SHADE



A | 43710 CLP
Wall Sconce



B | 43709 CLP
Foyer Pendant



Off White Fabric Shade

Shown as Pendant - 49.25" H.

CONVERTIBLE

Create two distinct lighting options with one fixture:
Pendant or Semi Flush.

C | 43706 CLP



Shown as Chandelier - 50.25" H.

CONVERTIBLE

Create two distinct lighting options with one fixture:
Chandelier or Semi Flush.

D | 43707 CLP



Shown as Semi Flush - 11.25" H.

Satin Etched Glass Diffuser



Shown as Semi Flush - 12.25" H.

EMORY

	ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/STEM	EXT.	HCWO	NOTES
A	43710	CLP	(2) 60W (C)	8.5	15.5	---	---	---	5.25	9	Ⓧ
B	43709	CLP	(4) 60W (C)	15	27.5	68	46	36	---	---	Additional chain 2996 CLP.
C	43706	CLP	(3) 100W (M)	18	10.25	49	67	36	---	---	Ⓧ (23-30W CFL) Additional chain 2996 CLP.
D	43707	CLP	(4) 100W (M)	24	11.5	50	66	36	---	---	Additional chain 2996 CLP.

Measurements shown in inches. U.S. & Canada Patent Pending.

EMORY

OLDE BRONZE® FINISH WITH CLEAR GLASS
OR OFF WHITE FABRIC SHADE



A | 43710 OZ
Wall Sconce

Clear Glass



B | 43709 OZ
Foyer Pendant



Off White Fabric Shade

Shown as Pendant - 49.25" H.

CONVERTIBLE

Create two distinct lighting options with one fixture: Pendant or Semi Flush.

C | 43706 OZ



Shown as Semi Flush - 11.25" H.



Shown as Chandelier - 50.25" H.

CONVERTIBLE

Create two distinct lighting options with one fixture: Chandelier or Semi Flush.

D | 43707 OZ



Satin-Etched Glass Diffuser

Shown as Semi Flush - 12.25" H.

EMORY

	ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/STEM	EXT.	HCWO	NOTES
A	43710	OZ	(2) 60W (C)	8.5	15.5	---	---	---	5.25	9	D
B	43709	OZ	(4) 60W (C)	15	27.5	68	46	36	---	---	Additional chain 2996 OZ, additional stem (12") 2999 OZ.
C	43706	OZ	(3) 100W (M)	18	10.25	49	67	36	---	---	(23-30W CFL) Additional chain 2996 OZ, additional stem (12") 2999 OZ.
D	43707	OZ	(4) 100W (M)	24	11.5	50	66	36	---	---	Additional chain 2996 OZ, additional stem (12") 2999 OZ.

Measurements shown in inches. U.S. & Canada Patent Pending.

EVIE

BRUSHED NICKEL FINISH WITH CLEAR OUTER
GLASS & ANTIQUE MERCURY INNER GLASS



A | 43627 NI
Pendant

Gray Cloth
Covered Cord



B | 43628 NI
Linear Chandelier



VINTAGE
FILAMENT
BULB

SOLD SEPARATELY
60W Medium Base
4071 CLR



C | 43624 NI
Mini Pendant



D | 43629 NI
Mini Pendant



E | 43625 NI
Mini Pendant

EVIE

	ITEM #	FINISH	INCAND. BULB	W	H	OVRLL. H	L	NOTES
A	43627	NI	(3) 100W (M) A19	14.25	9.5	113	---	
B	43628	NI	(6) 100W (M) A19	10	9.5	113	34.25	
C	43624	NI	(1) 100W (M) A19	6.5	7.75	113	---	
D	43629	NI	(1) 100W (M) A19	6	8.25	113	---	
E	43625	NI	(1) 100W (M) A19	6	9.5	113	---	

Measurements shown in inches. U.S. & Canada Patent Pending.

CIRCOLO

BRUSHED NICKEL FINISH WITH CLEAR GLASS
OUTER CYLINDERS & SATIN ETCHED
GLASS INNER CYLINDERS



A | 2347 NI
Chandelier



B | 2344 NI
Chandelier



C | 2346 NI
Chandelier

CIRCOLO

ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	STEM TILT	EXTRA WIRE	CHAIN/STEM	NOTES	
A	2347	NI	(12) 60W (M) T10	44.5	41	79	45°(12:12)	70	36	Additional stem 2999 (12") NI and/or 2997 (24") NI.
B	2344	NI	(6) 60W (M) T10	26	26.5	65	45°(12:12)	38	36	Additional stem 2999 (12") NI and/or 2997 (24") NI.
C	2346	NI	(9) 60W (M) T10	36	35.5	110	45°(12:12)	79	36	Additional stem 2999 (12") NI and/or 2997 (24") NI.

Measurements shown in inches. U.S. & Canada Patent Pending.




D | 6144 NI
Wall Sconce



E | 2343 NI
Mini Chandelier



F | 2345 NI
Oval Chandelier



G | 2943 NI
Linear Chandelier

CIRCOLO

	ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	L	STEM TILT	EXTRA WIRE	CHAIN/STEM	EXT.	HCWO	NOTES
D	6144	NI	(1) 60W (M) T10	4.5	10	---	---	---	---	---	6	5	Ⓧ
E	2343	NI	(3) 60W (M) T10	22	21.5	60	---	45°(12:12)	51	36	---	---	Additional stem 2999 (12") NI and/or 2997 (24") NI.
F	2345	NI	(8) 60W (M) T10	25	27	65	40.25	45°(12:12)	93	36	---	---	Additional stem 2999 (12") NI and/or 2997 (24") NI.
G	2943	NI	(8) 60W (M) T10	14.25	39.25	---	36.25	---	82	---	---	---	Additional chain 2996 NI.

Measurements shown in inches. U.S. & Canada Patent Pending.

CIRCOLO

OLDE BRONZE® FINISH WITH CLEAR GLASS
OUTER CYLINDERS & UMBER ETCHED GLASS
INNER CYLINDERS



B | 2344 OZ
Chandelier



A | 2347 OZ
Chandelier



C | 2346 OZ
Chandelier

CIRCOLO

ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	STEM TILT	EXTRA WIRE	CHAIN/STEM	NOTES	
A	2347	OZ	(12) 60W (M) T10	44.5	41	79	45°(12:12)	70	36	Additional stem 2999 (12") OZ.
B	2344	OZ	(6) 60W (M) T10	26	26.5	65	45°(12:12)	38	36	Additional stem 2999 (12") OZ.
C	2346	OZ	(9) 60W (M) T10	36	35.5	110	45°(12:12)	79	36	Additional stem 2999 (12") OZ.

Measurements shown in inches. U.S. & Canada Patent Pending.




D | 6144 OZ
Wall Sconce



E | 2343 OZ
Mini Chandelier



F | 2345 OZ
Oval Chandelier



G | 2943 OZ
Linear Chandelier

CIRCOLO

	ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	L	STEM TILT	EXTRA WIRE	CHAIN/STEM	EXT.	HCWO	NOTES
D	6144	OZ	(1) 60W (M) T10	4.5	10	---	---	---	---	---	6	5	D
E	2343	OZ	(3) 60W (M) T10	22	21.5	60	---	45°(12:12)	51	36	---	---	Additional stem 2999 (12") OZ.
F	2345	OZ	(8) 60W (M) T10	25	27	65	40.25	45°(12:12)	93	36	---	---	Additional stem 2999 (12") OZ.
G	2943	OZ	(8) 60W (M) T10	14.25	39.25	---	36.25	---	82	---	---	---	Additional chain 2996 OZ.

Measurements shown in inches. U.S. & Canada Patent Pending.

HENDRIK™

OLDE BRONZE® FINISH WITH
LIGHT UMBER ETCHED GLASS



B | 1873 OZ
Chandelier



A | 1675 OZ
Chandelier



C | 1884 OZ
Grand Chandelier

MATCHING BATH

See matching
bath fixtures
on page 441.




HENDRIK™

	ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/ STEM	NOTES
A	1675	OZ	(15) 75W (M)	42.25	36	110	68	72	ⓘ (18-25W CFL) Additional chain 4909 OZ.
B	1873	OZ	(18) 60W (M)	50.25	41.5	116	108	72	ⓘ (18-25W CFL) Additional chain 4909 OZ.
C	1884	OZ	(24) 60W (M)	55	47.5	122	114	72	ⓘ (18-25W CFL) Additional chain 4909 OZ.

Measurements shown in inches. U.S. & Canada Patent Pending.



D | 1672 OZ
Chandelier



E | 3275 OZ
Pendant

MATCHING MIRROR

41071 OZ
See page 413 or
kichler.com.



F | 1674 OZ
Chandelier



G | 1673 OZ
Oval Chandelier



HENDRIK™

	ITEM #	FINISH	INCAND. BULB	W	H	OVRL H	L	STEM TILT	EXTRA WIRE	NOTES
D	1672	OZ	(5) 100W (M)	24.5	21.5	60	---	45°(12:12)	68	Ⓜ (18-25W CFL) Additional stem 2999 (12") OZ.
E	3275	OZ	(3) 100W (M)	24	21.75	60	---	45°(12:12)	104	Ⓜ (18-25W CFL) Additional stem 2999 (12") OZ.
F	1674	OZ	(9) 100W (M)	33.25	25.75	64	---	45°(12:12)	104	Ⓜ (18-25W CFL) Additional stem 2999 (12") OZ.
G	1673	OZ	(6) 100W (M)	18	22.75	61	35.75	45°(12:12)	104	Ⓜ (18-25W CFL) Additional stem 2999 (12") OZ.

Measurements shown in inches. U.S. & Canada Patent Pending; E.G. U.S. Design Patent No. D577,850: D, F.

HENDRIK™

OLDE BRONZE® FINISH WITH
LIGHT UMBER ETCHED GLASS

COORDINATING CEILING FAN

See the full line of Kichler®
Ceiling Fans in catalog K416
or visit kichler.com.

C | 300114 OZ



A | 5076 OZ
Wall Sconce



B | 3677 OZ
Semi Flush



D | 3674 OZ
Semi Flush



E | 3475 OZ
Mini Pendant



F | 1687 OZ
Mini Pendant



G | 1671 OZ
Chandelier

HENDRIK™

ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	STEM TILT	EXTRA WIRE	EXT.	HCWO	NOTES	
A	5076	OZ	(1) 100W (M)	5.25	12	---	---	---	8	6	Ⓛ (18-25W CFL) May be installed with glass up or down.
B	3677	OZ	(4) 100W (M) ✓	24	12.25	---	---	---	---	---	Ⓛ (23-30W CFL)
C	300114	OZ	---	---	---	---	---	---	---	---	See the full line of Kichler® Ceiling Fans in catalog K416 or visit kichler.com.
D	3674	OZ	(2) 60W (M)	15	10	---	---	---	---	---	Ⓛ (13-15W CFL)
E	3475	OZ	(1) 100W (M)	5.25	7.5	46	---	62	---	---	Ⓛ (18-25W CFL) Additional chain 2996 OZ, additional stem 2999 (12") OZ. Sloped ceiling kit included.
F	1687	OZ	(1) 100W (M)	8	8.75	47	---	67	---	---	Ⓛ (23-30W CFL) Additional chain 2996 OZ, additional stem 2999 (12") OZ. Sloped ceiling kit included.
G	1671	OZ	(3) 100W (M)	19	16.75	55	45°(12:12)	68	---	---	Ⓛ (18-25W CFL) Additional stem 2999 (12") OZ.

Measurements shown in inches. U.S. Design Patent No. D705,907: G. U.S. & Canada Patent Pending: B, C, D, E, F.

HENDRIK™

BRUSHED NICKEL FINISH WITH
SATIN ETCHED CASED OPAL GLASS



A | 1873 NI
Chandelier



B | 1675 NI
Chandelier



C | 1884 NI
Grand Chandelier

MATCHING BATH

See matching
bath fixtures
on page 440.



HENDRIK™

	ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/ STEM	NOTES
A	1873	NI	(18) 60W (M)	50.25	41.5	116	108	72	ⓘ (18-25W CFL) Additional chain 4909 NI.
B	1675	NI	(15) 75W (M)	42.25	36	110	68	72	ⓘ (18-25W CFL) Additional chain 4909 NI.
C	1884	NI	(24) 60W (M)	55	47.5	122	114	72	ⓘ (18-25W CFL) Additional chain 4909 NI.

Measurements shown in inches. U.S. & Canada Patent Pending.

HENDRIK™

BRUSHED NICKEL FINISH WITH
SATIN ETCHED CASED OPAL GLASS



A | 1672 NI
Chandelier



B | 3275 NI
Pendant

MATCHING MIRROR


41071 NI
See page 413 or
kichler.com.



C | 1674 NI
Chandelier



D | 1673 NI
Oval Chandelier



COORDINATING CEILING FAN

See the full line of Kichler®
Ceiling Fans in catalog K416
or visit kichler.com.

E | 300114 NI



F | 5076 NI
Wall Sconce



G | 3677 NI
Semi Flush



H | 3674 OZ
Semi Flush



J | 3475 NI
Mini Pendant



K | 1687 NI
Mini Pendant



L | 1671 NI
Chandelier

HENDRIK™

ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	L	STEM TILT	EXTRA WIRE	CHAIN/ STEM	EXT.	HCWO	NOTES	
A	1672	NI	(5) 100W (M)	24.5	21.5	60	---	45°(12:12)	68	36	---	---	Ⓜ (18-25W CFL) Additional stem 2999 (12") NI and/or 2997 (24") NI.
B	3275	NI	(3) 100W (M)	24	21.75	60	---	45°(12:12)	104	36	---	---	Ⓜ (18-25W CFL) Additional stem 2999 (12") NI and/or 2997 (24") NI.
C	1674	NI	(9) 100W (M)	33.25	25.75	64	---	45°(12:12)	104	36	---	---	Ⓜ (18-25W CFL) Additional stem 2999 (12") NI and/or 2997 (24") NI.
D	1673	NI	(6) 100W (M)	18	22.75	61	35.75	45°(12:12)	104	36	---	---	Ⓜ (18-25W CFL) Additional stem 2999 (12") NI and/or 2997 (24") NI.
E	300114	NI	---	---	---	---	---	---	---	---	---	---	See the full line of Kichler® Ceiling Fans in catalog K416 or visit kichler.com .
F	5076	NI	(1) 100W (M)	5.25	12	---	---	---	---	8	6	Ⓜ Ⓜ (18-25W CFL) May be installed with glass up or down.	
G	3677	NI	(4) 100W (M) ✓	24	12.25	---	---	---	---	---	---	---	Ⓜ (23-30W CFL)
H	3674	NI	(2) 60W (M)	15	10	---	---	---	---	---	---	---	Ⓜ (13-15W CFL)
J	3475	NI	(1) 100W (M)	5.25	7.5	46	---	---	62	36	---	---	Ⓜ (18-25W CFL) Additional chain 2996 NI additional stem 2999 (12") OZ, and/or 2997 (24") NI. Sloped ceiling kit included.
K	1687	NI	(1) 100W (M)	8	8.75	47	---	---	67	36	---	---	Ⓜ (23-30W CFL) Additional chain 2996 NI, additional stem 2999 (12") OZ, and/or 2997 (24") NI. Sloped ceiling kit included.
L	1671	NI	(3) 100W (M)	19	16.75	55	---	45°(12:12)	68	36	---	---	Ⓜ (18-25W CFL) Additional stem 2999 (12") NI and/or 2997 (24") NI.

Measurements shown in inches. U.S. Patent Design No. D705,907: L. U.S. & Canada Patent Pending: E, G, H, J, K.

IMOGEN


OLDE BRONZE® FINISH



VINTAGE
FILAMENT
BULB

SOLD SEPARATELY
40W Candelabra Base
5971 CLR

A | 43732 OZ
Linear Chandelier
NOT TO SCALE



B | 43733 OZ
Mini Pendant



C | 43734 OZ
Pendant



D | 43731 OZ
Large Foyer Pendant

IMOGEN

	ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	L	STEM TILT	EXTRA WIRE	CHAIN/STEM	NOTES
A	43732	OZ	(5) 25W (C) / 40W T Type / 60W B Type / G Type	3.75	20.5	58	36	---	38	36	Additional chain 2996 OZ, additional stem 2999 (12") OZ. Sloped ceiling kit included.
B	43733	OZ	(1) 25W (C) / 40W T Type / 60W B Type / G Type	3	10.75	49	10	90°	46	36	Additional stem 2999 (12") OZ.
C	43734	OZ	(3) 25W (C) / 40W T Type / 60W B Type / G Type	4	18.75	57	18	---	38	36	Additional chain 2996 OZ, additional stem 2999 (12") OZ. Sloped ceiling kit included.
D	43731	OZ	(3) 25W (C) / 40W T Type / 60W B Type / G Type	3.75	30.75	69	17.5	---	24	36	Additional chain 2996 OZ, additional stem 2999 (12") OZ. Sloped ceiling kit included.

Measurements shown in inches. U.S. & Canada Patent Pending.

KRASI™

WARM BRONZE FINISH WITH CLEAR ETCHED
TEMPERED GLASS & OFF-WHITE FABRIC SHADES



Off-White
Fabric Shade

A | 42465 WMZ
Chandelier/Pendant

Satin Etched
Glass Diffuser

Off-White
Fabric Shade**B** | 42479 WMZ
Flush MountSatin Etched Cased
Opal GlassShown as
Semi Flush - 11.75" H.**PENDALETTE®**

Create three distinct lighting options with
one fixture: Semi Flush, Mini Pendant or
Wall Mount.

D | 42467 WMZShown as
Mini Pendant - 11" H.Satin Etched Cased
Opal Glass**C** | 42466 WMZ
PendantSatin Etched Cased
Opal GlassShown as
Wall Mount - 15.75" H.**KRASI™**

	ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/ STEM	EXT.	HCWO	NOTES
A	42465	WMZ	(4) 100W (M)	24	9.5	48	74	36	---	---	☑ (23-30W CFL) Additional chain 2996 WMZ, additional stem 2999 (12") WMZ. Sloped ceiling kit included.
B	42479	WMZ	(3) 60W (M)	16	7.75	---	---	---	---	---	☑ (13-15W CFL)
C	42466	WMZ	(1) 100W (M)	7.75	16.25	55	71	36	---	---	☑ (23-30W CFL) Additional chain 2996 WMZ, additional stem 2999 (12") WMZ. Sloped ceiling kit included.
D	42467	WMZ	(1) 100W (M)	5.5	11	54	67	36	6.5	2.5	☑ (23-30W CFL) Additional stem 2999 (12") WMZ.

Measurements shown in inches. U.S. & Canada Patent Pending.


TREMBA™

OLDE BRONZE® FINISH WITH
WHITE FABRIC SHADE &
SATIN ETCHED GLASS DIFFUSER



Satin Etched
Glass Diffuser

A | 43370 OZ
Oval Chandelier/Pendant
NOT TO SCALE



CONVERTIBLE

Create two distinct lighting options with one fixture:
Semi Flush or Mini Pendant.

B | 43371 OZ



CONVERTIBLE

Create two distinct lighting options with one fixture:
Pendant or Semi Flush.

C | 43373 OZ



TREMBA™

	ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	L	EXTRA WIRE	CHAIN/STEM	NOTES
A	43370	OZ	(6) 100W (M)	20	8.75	47	36	65	36	(23-30W CFL) Add. chain 2996 OZ, add. stem 2999 (12") OZ. Sloped ceiling kit incl.
B	43371	OZ	(1) 100W (M)	6.25	12.25	50	---	60	36	(23-30W CFL) Add. chain 2996 OZ, add. stem 2999 (12") OZ. Sloped ceiling kit incl.
C	43373	OZ	(4) 100W (M)	20	12.25	50	---	60	36	(23-30W CFL) Add. chain 2996 OZ, add. stem 4935 (12") OZ. Sloped ceiling kit incl.

Measurements shown in inches. U.S. & Canada Patent Pending.

MOXIE™

CAMBRIDGE BRONZE & GOLD FINISH WITH
LINEN FABRIC SHADE &
SATIN ETCHED GLASS DIFFUSER



A | 42099 CMZ
Linear Chandelier
NOT TO SCALE

MOXIE™

ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	L	EXTRA WIRE	CHAIN/STEM	NOTES	
A	42099	CMZ	(4) 100W (M)	16	13.5	40	48	110	36	☑ (23-30W CFL) Add. chain 2996 CMZ, add. stem 2999 (12") CMZ. Sloped ceiling kit included. Height includes one 6" stem.
B	42097	CMZ	(2) 100W (M)	16	12.75	---	---	---	---	☑ (23-30W CFL)
C	42073	CMZ	(4) 100W (M)	16	31	63	---	67	36	☑ (23-30W CFL) Add. chain 4901 CMZ, add. stem 4935 (12") CMZ. Height includes one 6" stem.
D	42098	CMZ	(3) 100W (M)	24	14	47	---	65	36	☑ (23-30W CFL) Add. chain 2996 CMZ, add. stem 4935 (12") CMZ. Sloped ceiling kit included. Height includes one 6" stem.
E	42061	CMZ	(3) 100W (M)	12	13.5	46	36	106	36	☑ (23-30W CFL) Add. chain 2996 CMZ, add. stem 2999 (12") CMZ. Sloped ceiling kit included. Height includes one 6" stem.

Measurements shown in inches. U.S. & Canada Patent Pending.



B | 42097 CMZ
Semi Flush

Linen Fabric Shade



C | 42073 CMZ
Pendant



D | 42098 CMZ
Pendant



E | 42061 CMZ
Linear Chandelier

SALDANA™

CLASSIC PEWTER FINISH WITH SATIN ETCHED
CASED OPAL INNER GLASS & WHITE
TRANSLUCENT ORGANZA OUTER SHADES



A | 42920 CLP
Linear Chandelier





B | 42921 CLP
Chandelier

COORDINATING CEILING FAN

See the full line of Kichler®
Ceiling Fans in catalog K416
or visit kichler.com.

C | 300181 AP



CONVERTIBLE

Create two distinct lighting
options with one fixture:
Semi Flush or Mini Chandelier.

D | 42923 CLP



Shown as
Semi Flush - 14.25" H.



Shown as
Mini Chandelier - 14" H.

SALDANA™

ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	L	EXTRA WIRE	CHAIN/ STEM	NOTES	
A	42920	CLP	(5) 50W (G9)	8	13.25	42	39	98	36	Additional chain 2996 CLP, additional stem 2999 (12") CLP. Sloped ceiling included. Halogen light source. Height includes one 12" stem.
B	42921	CLP	(5) 50W (G9)	24	14.25	43	---	61	36	Additional chain 2996 CLP, additional stem 4935 (12") CLP. Sloped ceiling included. Halogen light source. Height includes one 12" stem.
C	300181	AP	---	52	---	---	---	78	---	See the full line of Kichler® Ceiling Fans in catalog K416 or visit kichler.com .
D	42923	CLP	(3) 50W (G9)	18	14	42	---	62	36	Additional chain 2996 CLP, additional stem 2999 (12") CLP. Sloped ceiling included. Halogen light source. Height includes one 12" stem.

Measurements shown in inches. U.S. & Canada Patent Pending.

KAILEY™

BRUSHED NICKEL FINISH WITH
SATIN ETCHED GLASS &
WHITE ORGANZA SHADES



A | 43437 NI
Linear Chandelier
NOT TO SCALE




B | 43442 NI
Mini Pendant



C | 43438 NI
Chandelier

KAILEY™

ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	L	STEM TILT	EXTRA WIRE	CHAIN/STEM	NOTES	
A	43437	NI	(3) 100W (M)	9	13	51	36	---	94	36	(23-30W CFL) Additional chain 2996 NI, additional stem 2999 (12") NI and/or 2997 (24") NI. Sloped ceiling kit included.
B	43442	NI	(1) 50W (G9) 	6	10	48	---	90°	63	36	Additional stem 2999 (12") NI and/or 2997 (24") NI. Halogen light source.
C	43438	NI	(4) 60W (C) G Type / B Type	25	13.25	52	---	---	64	36	Additional chain 2996 NI, additional stem 2999 (12") NI and/or 2997 (24") NI. G-type bulb recommended. Sloped ceiling kit included.

Measurements shown in inches. U.S. & Canada Patent Pending.

SILVER CORAL


CLASSIC PEWTER FINISH WITH WHITE FABRIC
SHADE & ETCHED GLASS DIFFUSER



A | 43348 CLP
Oval Chandelier/Pendant
NOT TO SCALE




B | 43349 CLP
Mini Pendant



C | 43347 CLP
Chandelier/Pendant

Etched
Glass Diffuser



CONVERTIBLE

Create two distinct lighting options with one fixture:
Semi Flush or Pendant.

D | 43346 CLP

Shown as
Semi Flush - 11.25" H.

Shown as
Pendant - 11.25" H.

SILVER CORAL

ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	L	EXTRA WIRE	CHAIN/STEM	NOTES	
A	43348	CLP	(4) 100W (M)	16	13.5	47	34	96	36	☑ (23-30W CFL) Add. chain 2996 CLP, add. stem 2999 (12") CLP. Sloped ceiling kit included.
B	43349	CLP	(1) 100W (M)	7.25	10	48	---	66	36	☑ (23-30W CFL) Add. chain 2996 CLP, add. stem 2999 (12") CLP. Sloped ceiling kit included.
C	43347	CLP	(4) 100W (M)	22	13.5	47	---	99	36	☑ (23-30W CFL) Add. chain 2996 CLP, add. stem 4935 (12") CLP. Sloped ceiling kit included.
D	43346	CLP	(3) 100W (M)	18.25	11.25	50	---	68	36	☑ (23-30W CFL) Add. chain 2996 CLP, add. stem 2999 (12") CLP. Sloped ceiling kit included.

Measurements shown in inches. U.S. & Canada Patent Pending.

JARDINE

POLISHED CHROME FINISH WITH SATIN ETCHED
CASED OPAL GLASS INNER DIFFUSERS & WHITE
TRANSLUCENT ORGANZA OUTER SHADES



Satin Etched
White Glass

A | 42391 CH
Chandelier/Pendant
NOT TO SCALE



B | 42306 CH
Semi Flush



C | 45293 CH



MULTI-POSITIONAL WALL FIXTURE

Two distinct lighting fixtures in one!
Fixture can be installed on the wall
horizontally or vertically.



D | 45291 CH
Wall Sconce

JARDINE

	ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/STEM	EXT.	HCWO	NOTES
A	42391	CH	(3) 100W (M)	24	27.5	102	51	72	---	---	Ⓜ (23-30W CFL) Additional chain 4901 CH.
B	42306	CH	(3) 60W (C)	15.5	10.75	---	---	---	---	---	
C	45293	CH	(4) 50W (G9) Ⓢ	36.5	4.5	---	---	---	4.25	2.25	Ⓢ Halogen light source.
D	45291	CH	(2) 50W (G9) Ⓢ	25	4.5	---	---	---	4.25	2.25	Ⓢ Halogen light source.

Measurements shown in inches. B,C: U.S. & Canada Patent Pending. D: U.S. Design Patent No.: D670,423.

CRYSTAL SKYE™

POLISHED CHROME FINISH
WITH OPTICAL CRYSTALS



A | 42175 CH
Wall Sconce
ADA Compliant



B | 42195 CH
Chandelier/Pendant

CRYSTAL SKYE™

	ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	L	EXTRA WIRE	EXT.	HCWO	NOTES
A	42175	CH	(1) 100W (M)	6.5	11.5	85	---	---	4	5.5	Ⓜ Halogen light source.
B	42195	CH	(8) 50W (G9) Ⓜ	20.75	5	53.5	---	---	---	---	Halogen light source.

Measurements shown in inches. U.S. & Canada Patent Pending.



C | 42174 CH
Mini Pendant



D | 42173 CH
Oval Chandelier/Pendant



CRYSTAL SKYE™

	ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	L	EXTRA WIRE	EXT.	HCWO	NOTES
C	42174	CH	(2) 50W (G9)	6.5	11	---	---	---	---	---	☑ (23-30W CFL)
D	42173	CH	(12) 50W (G9)	35.25	5	79	35.25	10	4	5.5	Halogen light source.

Measurements shown in inches. U.S. & Canada Patent Pending.

EMILE

OLDE BRONZE® FINISH WITH
PRISMATIC OPTICAL CRYSTAL ACCENTS



A | 43745 OZ
Linear Chandelier
NOT TO SCALE



Shown as
Pendant - 20" H.

CONVERTIBLE

Create two distinct lighting options with one fixture:
Pendant or Semi Flush.

B | 43748 OZ



Shown as
Semi Flush - 12" H.



C | 43747 OZ
Foyer Chandelier



Shown as
Pendant - 30" H.

CONVERTIBLE

Create two distinct lighting options with one fixture:
Pendant or Semi Flush.

E | 43750 OZ



D | 43749 OZ
Wall Sconce



Shown as
Semi Flush - 20.5" H.

EMILE

	ITEM #	FINISH	INCAND. BULB	W	H	OVRL H	L	EXTRA WIRE	CHAIN/STEM	EXT.	HCWO	NOTES
A	43745	OZ	(12) 60W (C) B Type / G Type / 40W T Type	13	29.5	106	37	52	72	---	---	Additional chain 4901 OZ.
B	43748	OZ	(1) 100W (M) A19 / 60W S21	12	20	94	---	29	72	---	---	Additional chain 2996 OZ.
C	43747	OZ	(9) 60W (C) B Type / G Type / 40W T Type	23.25	32.75	107	---	16	72	---	---	Additional chain 4901 OZ.
D	43749	OZ	(1) 100W (M) A19 / 60W S21	12	12	---	---	---	---	6	5.75	Ⓧ
E	43750	OZ	(9) 60W (C) B Type / G Type / 40W T Type ❖	18	30	104	---	20	72	---	---	Additional chain 2996 OZ.

Measurements shown in inches. U.S. & Canada Patent Pending.



Piper Wall Sconce 43727 ESP | Page 233 & Pendant 43723 ESP | Page 232

PIPER

ESPRESSO FINISH WITH ALTERNATING CLEAR
GLASS & ESPRESSO METAL RODS, ACCENTED
WITH CLEAR GLASS SPHERES



A | 43727 ESP
Wall Sconce



B | 43726 ESP
Semi Flush



C | 43725 ESP
Oval Chandelier/Pendant



D | 43758 ESP
Grand Chandelier



E | 43723 ESP
Chandelier/Pendant



F | 43724 ESP
Foyer Chandelier

PIPER

	ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	L	EXTRA WIRE	CHAIN/ STEM	EXT.	HCWO	NOTES
A	43727	ESP	(2) 40W (C) T Type / 60W B Type	8	12.25	---	---	---	---	4	4.75	Ⓛ
B	43726	ESP	(3) 60W (C) B Type / G Type / 40W T Type	15	14.25	---	---	---	---	---	---	
C	43725	ESP	(6) 60W (C) B Type / G Type / 40W T Type	13.5	11.75	51	36	100	36	---	---	Additional chain 4901 ESP, additional stem 2999 (12") ESP. Sloped ceiling kit included.
D	43758	ESP	(18) 60W (C)	22	69.75	143.75	---	58	72	---	---	Additional chain 4901 ESP.
E	43723	ESP	(6) 60W (C) B Type / G Type / 40W T Type	24	31.5	106	---	45	72	---	---	Additional chain 4901 ESP.
F	43724	ESP	(6) 60W (C) B Type / G Type / 40W T Type	16	33.5	108	---	15	72	---	---	Additional chain 4901 ESP.

Measurements shown in inches. U.S. & Canada Patent Pending.

PIPER

ESPRESSO FINISH WITH ALTERNATING CLEAR
GLASS & ESPRESSO METAL RODS, ACCENTED
WITH CLEAR GLASS SPHERES



A | 43723 ESP
Chandelier/Pendant



B | 43758 ESP
Grand Chandelier



C | 43724 ESP
Foyer Chandelier



D | 43725 ESP
Oval Chandelier/Pendant



E | 43726 ESP
Semi Flush



F | 43727 ESP
Wall Sconce

PIPER

	ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	L	EXTRA WIRE	CHAIN/STEM	EXT.	HCWO	NOTES
A	43723	ESP	(6) 60W (C) B Type / G Type / 40W T Type	24	31.5	106	---	45	72	---	---	Additional chain 4901 ESP.
B	43758	ESP	(18) 60W (C)	22	69.75	143.75	---	58	72	---	---	Additional chain 4901 ESP.
C	43724	ESP	(6) 60W (C) B Type / G Type / 40W T Type	16	33.5	108	---	15	72	---	---	Additional chain 4901 ESP.
D	43725	ESP	(6) 60W (C) B Type / G Type / 40W T Type	13.5	11.75	51	36	100	36	---	---	Additional chain 4901 ESP, additional stem 2999 (12") ESP. Sloped ceiling kit included.
E	43726	ESP	(3) 60W (C) B Type / G Type / 40W T Type	15	14.25	---	---	---	---	---	---	
F	43727	ESP	(2) 40W (C) T Type / 60W B Type	8	12.25	---	---	---	---	4	4.75	♿

Measurements shown in inches. U.S. & Canada Patent Pending.

CRYSTAL PERSUASION™

POLISHED CHROME FINISH WITH
WHITE LINEN FABRIC SHADES,
SATIN ETCHED GLASS DIFFUSERS &
OPTICAL CRYSTAL ACCENTS



A | 42031 CH
Chandelier



B | 42030 CH
Chandelier

CRYSTAL PERSUASION™

	ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/STEM	NOTES
A	42031	CH	(9) 60W (C)	37	31.5	106	56	72	Additional chain 4901 CH. G Type bulb recommended.
B	42030	CH	(5) 60W (C)	30	21	95	56	72	Additional chain 2996 CH. G Type bulb recommended.

Measurements shown in inches. U.S. & Canada Patent Pending.

CRYSTAL PERSUASION™

POLISHED CHROME FINISH WITH
WHITE LINEN FABRIC SHADES,
SATIN ETCHED GLASS DIFFUSERS &
OPTICAL CRYSTAL ACCENTS



Satin Etched
Glass Diffuser

A | 42034 CH
Pendant



B | 42028 CH
Wall Sconce



C | 42035 CH
Semi Flush



D | 42029 CH
Mini Chandelier

CRYSTAL PERSUASION™

ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/STEM	EXT.	HCWO	NOTES
A	CH	(3) 100W (M)	24	21	95	22	72	---	---	☑ (23-30W CFL) Additional chain 2996 CH.
B	CH	(1) 60W (C) G Type	8.5	9	---	---	---	7.5	4.75	G Type bulb required.
C	CH	(3) 100W (M)	15	11.5	---	---	---	---	---	☑ (23-30W CFL)
D	CH	(5) 60W (C) ⚡	17	13.75	52	159	36	---	---	Additional chain 2996 CH. Krypton light source.

Measurements shown in inches. U.S. & Canada Patent Pending.

PARKER POINT™

POLISHED CHROME FINISH WITH
ORGANZA WRAPPED FABRIC SHADES
& OPTICAL CRYSTAL ACCENTS



Optical Crystal
Accents

A | 42633 CH
Chandelier
NOT TO SCALE



B | 42634 CH
Wall Sconce

Optical Crystal
Accents



C | 42631 CH
Chandelier

PARKER POINT™

	ITEM #	FINISH	INCAND. BULB	W	H	OVRLL. H	EXTRA WIRE	CHAIN/ STEM	EXT.	HCWO	NOTES
A	42633	CH	(9) 60W (C)	36	33.5	72	99	36	---	---	Additional chain 4901 CH, additional stem 4935 (12") CH. Sloped ceiling kit included.
B	42634	CH	(1) 60W (C)	6.75	15.5	---	---	---	8.5	10.25	D
C	42631	CH	(5) 60W (C)	26	24.5	63	61	36	---	---	Additional chain 2996 CH, additional stem 2999 (12") CH. Sloped ceiling kit included.

Measurements shown in inches. U.S. & Canada Patent Pending.

PARKER POINT™

POLISHED CHROME FINISH WITH
ORGANZA WRAPPED FABRIC SHADES
& OPTICAL CRYSTAL ACCENTS



Optical Crystal Column

Organza Wrapped
Fabric Shade

A | 42632 CH
Chandelier
NOT TO SCALE



CONVERTIBLE

Create two distinct lighting options with one fixture:
Mini Chandelier or Semi Flush..

B | 42630 CH

Shown as
Mini Chandelier - 17.75 H.

Shown as
Semi Flush - 18 H.

PARKER POINT™

	ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/STEM	NOTES
A	42632	CH	(8) 60W (C)	36	28	66	95	36	Additional chain 4901 CH, additional stem 4935 (12") CH. Sloped ceiling kit included.
B	42630	CH	(3) 60W (C)	17	17.75	56	13	36	Additional chain 2996 CH, additional stem 2999 (12") CH. Sloped ceiling kit included.

Measurements shown in inches. U.S. & Canada Patent Pending.

LEANORA™

POLISHED CHROME FINISH WITH
OPTICAL CRYSTAL CENTER COLUMN,
BOBECHES AND PENDALOGUES



A | 42544 CH
Chandelier/Dinette



B | 42546 CH
Chandelier



C | 42545 CH
Chandelier

LEANORA™

	ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/STEM	NOTES
A	42544	CH	(3) 60W (C)	21	24	98	60	72	Additional chain 2996 CH.
B	42546	CH	(9) 60W (C)	34	35	109	50	72	Additional chain 4901 CH.
C	42545	CH	(6) 60W (C)	28	28.75	103	55	72	Additional chain 4901 CH.

Measurements shown in inches. U.S. & Canada Patent Pending.

JULES™

POLISHED CHROME FINISH WITH
OPTICAL CRYSTAL ACCENTS



A | 43121 CH
Chandelier



B | 43124 CH
Chandelier

JULES™

	ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/ STEM	NOTES
A	43121	CH	(6) 60W (C)	25.25	23.75	98	65	72	Additional chain 2996 CH.
B	43124	CH	(12) 60W (C)	44	47	121	59	72	Additional chain 4901 CH.

Measurements shown in inches. U.S. & Canada Patent Pending.

BIRKDALE™

STERLING GOLD FINISH WITH
WRAPPED BEAD ACCENTS



A | 43811 SGD
Chandelier
NOT TO SCALE



B | 43813 SGD
Semi Flush



C | 43812 SGD
Chandelier

BIRKDALE™

	ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/STEM	NOTES
A	43811	SGD	(6) 60W (C)	24	37.75	112	46	72	Additional chain 2996 SGD.
B	43813	SGD	(3) 60W (C)	16.25	16.5	---	---	---	
C	43812	SGD	(8) 60W (C)	30.5	35.25	110	71	72	Additional chain 2996 SGD.

Measurements shown in inches. U.S. & Canada Patent Pending.



Rosalie Chandelier 43805 SGD | Page 247

ROSALIE

STERLING GOLD FINISH WITH
ANTIQUED MERCURY GLASS



A | 43805 SGD
Chandelier

ROSALIE

ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/ STEM	NOTES
A 43805	SGD	(8) 60W (C)	32	38.25	112	48	72	Additional chain 2996 SGD.

Measurements shown in inches. U.S. & Canada Patent Pending.

ROSALIE

STERLING GOLD FINISH WITH
ANTIQUED MERCURY GLASS



A | 43803 SGD
Mini Chandelier



B | 43804 SGD
Chandelier

ROSALIE

	ITEM #	FINISH	INCAND. BULB	W	H	OVRLL. H	EXTRA WIRE	CHAIN/STEM	NOTES
A	43803	SGD	(5) 60W (C)	17.75	26.75	101	20	72	Additional chain 2996 SGD.
B	43804	SGD	(5) 60W (C)	24.25	38	112	12	72	Additional chain 2996 SGD.

Measurements shown in inches. U.S. & Canada Patent Pending.

SAVANNA

STERLING GOLD FINISH WITH
ANTIQUED MERCURY GLASS



A | 43451 SGD
Pendant



B | 43452 SGD
Pendant

SAVANNA

	ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/ STEM	NOTES
A	43451	SGD	(4) 40W (C) B Type	19	31.5	106	29	72	Additional chain 2996 SGD.
B	43452	SGD	(1) 100W (M)	12	20.75	95	24	72	(23-30W CFL) Additional chain 2996 SGD.

Measurements shown in inches. U.S. & Canada Patent Pending.

SHELSLEY™

STERLING GOLD FINISH WITH
OPTICAL CRYSTAL ACCENTS



A | 43690 SGD
Grand Chandelier
NOT TO SCALE



B | 43623 SGD
Wall Sconce



C | 43622 SGD
Foyer Pendant



D | 43619 SGD
Foyer Chandelier



E | 43620 SGD
Chandelier



F | 43621 SGD
Chandelier

SHELSLEY™

	ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/STEM	EXT.	HCWO	NOTES
A	43690	SGD	(12) 60W (C)	45	50	124	71	72	---	---	Additional chain 2996 SGD.
B	43623	SGD	(2) 60W (C) B Type / G Type	11.75	18	---	---	---	6	9.75	D
C	43622	SGD	(3) 60W (C) B Type / G Type	12	19	93	24	72	---	---	Additional chain 2996 SGD.
D	43619	SGD	(4) 60W (C) B Type / G Type	19.5	33.5	108	17	72	---	---	Additional chain 2996 SGD.
E	43620	SGD	(5) 60W (C) B Type / G Type	26.5	35	110	34	72	---	---	Additional chain 2996 SGD.
F	43621	SGD	(8) 60W (C) B Type / G Type	36	40.25	114	70	72	---	---	Additional chain 2996 SGD.

Measurements shown in inches. U.S. & Canada Patent Pending.

ABELLONA™

STERLING GOLD™ FINISH WITH
CRYSTAL BEAD ACCENTS



A | 43609 SGD
Chandelier
NOT TO SCALE



B | 43610 SGD
Wall Sconce



C | 43607 SGD
Mini Chandelier



D | 43608 SGD
Chandelier


ABELLONA™

ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/STEM	EXT.	HCWO	NOTES
A	SGD	(8) 60W (C) B Type / 40W T Type	30	40	114	68	72	---	---	Additional chain 2996 SGD.
B	SGD	(1) 60W (C) B Type / 40W T Type	5.75	10.5	---	---	---	6.5	5.5	D
C	SGD	(5) 60W (C) B Type / 40W T Type	18	24	98	33	72	---	---	Additional chain 2996 SGD.
D	SGD	(6) 60W (C) B Type / 40W T Type	25	33	107	32	72	---	---	Additional chain 2996 SGD.

Measurements shown in inches. U.S. & Canada Patent Pending.

GRACE

STERLING GOLD FINISH WITH
OPTICAL CRYSTAL ACCENTS



Carved Crystal
Accents

A | 43729 SGD
Chandelier
NOT TO SCALE



B | 43728 SGD
Chandelier

GRACE

	ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/ STEM	NOTES
A	43729	SGD	(9) 60W (C)	30	31	105	54	72	Additional chain 2996 SGD.
B	43728	SGD	(5) 60W (C)	25	26.5	101	22.5	72	Additional chain 2996 SGD.

Measurements shown in inches. U.S. & Canada Patent Pending.



Casilda™ Chandelier 43565 SGD | Page 259 & Mini Pendant 43568 SGD | Page 259

CASILDA™

STERLING GOLD OR OLDE BRONZE® FINISH WITH
OPTICAL CRYSTAL ACCENTS & SILVER BEIGE
FABRIC SHADES



A | 43569 SGD
Oval Chandelier



B | 43566 SGD
Pendant



C | 43565 SGD
Chandelier



D | 43568 SGD
Mini Pendant



E | 43567 SGD
Semi Flush



F | 43570 SGD
Wall Sconce

CASILDA™

ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	L	STEM TILT	EXTRA WIRE	CHAIN/STEM	EXT.	HCWO	NOTES	
A	43569	SGD	(6) 100W (M)	23	25.75	64	40	---	99	36	---	---	⚡ (18-25W CFL) Additional chain 2996 SGD, additional stem 2999 (12") SGD. Sloped ceiling kit included.
B	43566	SGD	(3) 100W (M)	22	26.75	65	---	---	54	36	---	---	⚡ (23-30W CFL) Additional chain 2996 SGD, additional stem 2999 (12") SGD. Sloped ceiling kit included.
C	43565	SGD	(4) 100W (M)	29	25.5	64	---	---	61	36	---	---	⚡ (18-25W CFL) Additional chain 2996 SGD, additional stem 2999 (12") SGD. Sloped ceiling kit included.
D	43568	SGD	(1) 100W (M)	7	13.5	52	---	90°	61	36	---	---	⚡ (23-30W CFL) Additional stem 2999 (12") SGD.
E	43567	SGD	(3) 100W (M)	16	12.5	---	---	---	---	---	---	---	⚡ (23-30W CFL)
F	43570	SGD	(1) 100W (M)	13.5	16	---	---	---	---	---	8.25	7.5	⚡ (18-25W CFL)

Measurements shown in inches. U.S. & Canada Patent Pending.

CASILDA™

STERLING GOLD™ FINISH WITH OPTICAL CRYSTAL
ACCENTS & SILVER BEIGE FABRIC SHADES



MATCHING BATH

See matching
bath fixtures
on page 445.



A | 43569 SGD
Oval Chandelier
NOT TO SCALE



B | 43568 SGD
Mini Pendant



C | 43570 SGD
Wall Sconce



Satin Etched
Glass Diffuser

D | 43567 SGD
Semi Flush



Cut, Polished and
Faceted Crystal

E | 43566 SGD
Pendant



F | 43565 SGD
Chandelier

CASILDA™

ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	L	STEM TILT	EXTRA WIRE	CHAIN/STEM	EXT.	HCWO	NOTES	
A	43569	SGD	(6) 100W (M)	23	25.75	64	40	---	99	36	---	---	⊗ (18-25W CFL) Additional chain 2996 SGD, additional stem 2999 (12") SGD. Sloped ceiling kit included.
B	43568	SGD	(1) 100W (M)	7	13.5	52	---	90°	61	36	---	---	⊗ (23-30W CFL) Additional stem 2999 (12") SGD.
C	43570	SGD	(1) 100W (M)	13.5	16	---	---	---	---	---	8.25	7.5	⊗ (18-25W CFL)
D	43567	SGD	(3) 100W (M)	16	12.5	---	---	---	---	---	---	---	⊗ (23-30W CFL)
E	43566	SGD	(3) 100W (M)	22	26.75	65	---	---	54	36	---	---	⊗ (23-30W CFL) Additional chain 2996 SGD, additional stem 2999 (12") SGD. Sloped ceiling kit included.
F	43565	SGD	(4) 100W (M)	29	25.5	64	---	---	61	36	---	---	⊗ (18-25W CFL) Additional chain 2996 SGD, additional stem 2999 (12") SGD. Sloped ceiling kit included.

Measurements shown in inches. U.S. & Canada Patent Pending.

CASILDA™

OLDE BRONZE® FINISH WITH OPTICAL CRYSTAL
ACCENTS & SILVER BEIGE FABRIC SHADES



MATCHING BATH

See matching
bath fixtures
on page 444.



A | 43569 OZ
Oval Chandelier
NOT TO SCALE



B | 43568 OZ
Mini Pendant



C | 43570 OZ
Wall Sconce



D | 43567 OZ
Semi Flush

Satin Etched
Glass Diffuser



E | 43566 OZ
Pendant



F | 43565 OZ
Chandelier

CASILDA™

ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	L	STEM TILT	EXTRA WIRE	CHAIN/STEM	EXT.	HCWO	NOTES	
A	43569	OZ	(6) 100W (M)	23	25.75	64	40	---	99	36	---	---	Ⓢ (18-25W CFL) Additional chain 2996 OZ, additional stem 2999 (12") OZ. Sloped ceiling kit included.
B	43568	OZ	(1) 100W (M)	7	13.5	52	---	90°	61	36	---	---	Ⓢ (23-30W CFL) Additional stem 2999 (12") OZ.
C	43570	OZ	(1) 100W (M)	13.5	16	---	---	---	---	---	8.25	7.5	Ⓢ (18-25W CFL)
D	43567	OZ	(3) 100W (M)	16	12.5	---	---	---	---	---	---	---	Ⓢ (23-30W CFL)
E	43566	OZ	(3) 100W (M)	22	26.75	65	---	---	54	36	---	---	Ⓢ (23-30W CFL) Additional chain 2996 OZ, additional stem 2999 (12") OZ. Sloped ceiling kit included.
F	43565	OZ	(4) 100W (M)	29	25.5	64	---	---	61	36	---	---	Ⓢ (18-25W CFL) Additional chain 2996 OZ, additional stem 2999 (12") OZ. Sloped ceiling kit included.

Measurements shown in inches. U.S. & Canada Patent Pending.

LEIGHTON™

OLDE BRONZE® FINISH WITH OFF-WHITE
FABRIC SHADES, SATIN ETCHED GLASS DIFFUSERS
& OPTICAL CRYSTAL DISCS



Satin Etched
Glass Diffuser

A | 42482 OZ
Pendant



B | 42476 OZ
Chandelier



Optical Crystal Discs

C | 42478 OZ
Chandelier



D | 45178 OZ
Wall Sconce



E | 42484 OZ
Mini Pendant



F | 42485 OZ
Semi Flush



G | 42486 OZ
Semi Flush

LEIGHTON™

ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/STEM	EXT.	HCWO	NOTES	
A	42482	OZ	(3) 100W (M)	26	28	102	47	72	---	☑ (23-30W CFL) Add. chain 2996 OZ. Satin Etched glass glare shield.	
B	42476	OZ	(5) 60W (C)	31	28.5	103	43	72	---	Add. chain 2996 OZ. Krypton or G type bulb recommended.	
C	42478	OZ	(9) 60W (C)	36	35.75	110	47	72	---	Add. chain 4901 OZ. Krypton or G type bulb recommended.	
D	45178	OZ	(1) 60W (C)	8	14.75	---	---	---	9.75	8.75	Krypton or G Type bulb recommended.
E	42484	OZ	(1) 60W (C) ⚡	8	18.5	56.5	50	36	---	---	Add. chain 2996 OZ, add. stem 2999 (12") OZ. Krypton light source. Sloped ceiling kit incl.
F	42485	OZ	(3) 75W (M)	16	11	---	---	---	---	---	☑ (23-30W CFL)
G	42486	OZ	(4) 100W (M)	22	13.5	---	---	---	---	---	☑ (23-30W CFL)

Measurements shown in inches. U.S. & Canada Patent Pending.

LARA™

CLASSIC PEWTER FINISH WITH
CLEAR GLASS CYLINDERS & MOTTLED
WISPY WHITE GLASS DRIP CANDLES



B | 42861 CLP
Chandelier



A | 42863 CLP
Chandelier

Optical Crystal Accent



C | 42860 CLP
Chandelier/Dinette



D | 42862 CLP
Oval Chandelier



LARA™

	ITEM #	FINISH	INCAND. BULB	W	H	OVRL H	L	EXTRA WIRE	CHAIN/STEM	NOTES
A	42863	CLP	(9) 60W (C)	32	38.75	113	---	70	72	Additional chain 4901 CLP.
B	42861	CLP	(5) 60W (C)	26.75	32.5	107	---	35	72	Additional chain 2996 CLP.
C	42860	CLP	(3) 60W (C)	20	26.5	101	---	35	72	Additional chain 2996 CLP.
D	42862	CLP	(6) 60W (C)	18	33.5	108	36	70	72	Additional chain 2996 CLP.

Measurements shown in inches. U.S. & Canada Patent Pending.

LARA™

CLASSIC PEWTER FINISH WITH
CLEAR GLASS CYLINDERS & MOTTLED
WISPY WHITE GLASS DRIP CANDLES



A | 45362 CLP
Wall Sconce



B | 42864 CLP
Chandelier/Pendant



Clear Outside Glass
with Etched Bottom
and Inner Beige
Fabric Shade

C | 42866 CLP
Semi Flush



D | 42865 CLP
Mini Pendant

LARA™

ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	STEM TILT	EXTRA WIRE	CHAIN/STEM	EXT.	HCWO	NOTES
A	45362	CLP	(1) 60W (C)	4.75	16.25	---	---	---	6	9.25	D
B	42864	CLP	(3) 100W (M)	24	34	108	---	54	72	---	E (23-30W CFL) Additional chain 2996 CLP.
C	42866	CLP	(2) 100W (M)	21.25	18.75	---	---	---	---	---	E (23-30W CFL)
D	42865	CLP	(1) 60W (C)	8.75	19.5	58	45°(12:12)	52	36	---	Additional stem 2999 (12") CLP.

Measurements shown in inches. U.S. & Canada Patent Pending.

LARA™

SHADOW BRONZE™ FINISH
WITH CLEAR GLASS CYLINDERS &
BEIGE GLASS DRIP CANDLES



Optical Crystal Accent

A | 42863 SWZ
Chandelier



B | 42861 SWZ
Chandelier

LARA™

	ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/STEM	NOTES
A	42863	SWZ	(9) 60W (C)	32	38.75	113	70	72	Additional chain 4901 SWZ.
B	42861	SWZ	(5) 60W (C)	26.75	32.5	107	35	72	Additional chain 2996 SWZ.

Measurements shown in inches. U.S. & Canada Patent Pending.

LARA™


SHADOW BRONZE™ FINISH
WITH CLEAR GLASS CYLINDERS &
BEIGE GLASS DRIP CANDLES



A | 42860 SWZ
Chandelier/Dinette



B | 42862 SWZ
Oval Chandelier





C | 45362 SWZ
Wall Sconce



D | 42865 SWZ
Mini Pendant



Clear Outside Glass
with Etched Bottom
and Inner Beige
Fabric Shade

E | 42866 SWZ
Semi Flush



F | 42864 SWZ
Chandelier/Pendant

LARA™

	ITEM #	FINISH	INCAND. BULB	W	H	OVRL H	L	STEM TILT	EXTRA WIRE	CHAIN/STEM	EXT.	HCWO	NOTES
A	42860	SWZ	(3) 60W (C)	20	26.5	101	---	---	35	72	---	---	Additional chain 2996 SWZ.
B	42862	SWZ	(6) 60W (C)	18	33.5	108	36	---	70	72	---	---	Additional chain 2996 SWZ.
C	45362	SWZ	(1) 60W (C)	4.75	16.25	---	---	---	---	---	6	9.25	D
D	42865	SWZ	(1) 60W (C)	8.75	19.5	58	---	45°(12:12)	52	36	---	---	Additional stem 2999 (12") SWZ.
E	42866	SWZ	(2) 100W (M)	21.25	18.75	---	---	---	---	---	---	---	(23-30W CFL)
F	42864	SWZ	(3) 100W (M)	24	34	108	---	---	54	72	---	---	(23-30W CFL) Additional chain 2996 SWZ.

Measurements shown in inches. U.S. & Canada Patent Pending.

LACEY™

ANTIQUE PEWTER FINISH WITH
SATIN ETCHED CASED OPAL GLASS INNER
DIFFUSERS & WHITE TRANSLUCENT
ORGANZA OUTER SHADES



A | 42396 AP
Grand Chandelier



B | 42381 AP
Chandelier

COORDINATING CEILING FAN

See the full line of Kichler®
Ceiling Fans in catalog K416
or visit kichler.com.

C | 300181 AP



D | 42382 AP
Chandelier



E | 42383 AP
Chandelier

LACEY™

	ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/ STEM	NOTES
A	42396	AP	(18) 60W (C)	62	53	127	68	72	Additional chain 4901 AP.
B	42381	AP	(5) 60W (C)	25	25.75	100	28	72	Additional chain 2996 AP.
C	300181	AP	---	52	---	---	78	---	See the full line of Kichler® Ceiling Fans in catalog K416 or visit kichler.com .
D	42382	AP	(9) 60W (C)	34.25	29.5	104	65	72	Additional chain 4901 AP.
E	42383	AP	(12) 60W (C)	42	32	106	65	72	Additional chain 4901 AP.

Measurements shown in inches. U.S. & Canada Patent Pending.

LACEY™

ANTIQUE PEWTER FINISH WITH
SATIN ETCHED CASED OPAL GLASS INNER
DIFFUSERS & WHITE TRANSLUCENT
ORGANZA OUTER SHADES

MATCHING BATH

See matching
bath fixtures
on page 446.



A | 45281 AP
Wall Sconce



B | 42384 AP
Mini Pendant



C | 42386 AP
Semi Flush



D | 42399 AP
Semi FLush



E | 42387 AP
Semi Flush

Satin Etched
White Glass



F | 42385 AP
Pendant

LACEY™

ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	STEM TILT	EXTRA WIRE	CHAIN/STEM	EXT.	HCWO	NOTES
A	45281	AP	(1) 60W (C)	5	10.75	---	---	---	7	6.5	D
B	42384	AP	(1) 60W (C/K) D	6	10.25	49	90°	54	---	---	Additional stem 2999 (12") AP. Krypton bulb included.
C	42386	AP	(3) 100W (M)	15	10.75	---	---	---	---	---	D (18-25W CFL)
D	42399	AP	(5) 100W (M)	28	15.25	---	---	---	---	---	D (23-30W CFL)
E	42387	AP	(4) 100W (M)	20	13	---	---	---	---	---	D (23-30W CFL)
F	42385	AP	(4) 100W (M)	20	23.5	98	---	14	72	---	D (23-30W CFL) Additional chain 2996 AP.

Measurements shown in inches. U.S. & Canada Patent Pending.

LACEY™

MISSION BRONZE™ FINISH WITH
SATIN ETCHED CASED OPAL GLASS INNER
DIFFUSERS & LIGHT UMBER TRANSLUCENT
ORGANZA OUTER SHADES



A | 42396 MIZ
Grand Chandelier

LACEY™

ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/ STEM	NOTES
A 42396	MIZ	(18) 60W (C)	62	53	127	68	72	Additional chain 4901 MIZ.

Measurements shown in inches. U.S. & Canada Patent Pending.

LACEY™

MISSION BRONZE™ FINISH WITH
SATIN ETCHED CASED OPAL GLASS INNER
DIFFUSERS & LIGHT UMBER TRANSLUCENT
ORGANZA OUTER SHADES



A | 42381 MIZ
Chandelier

COORDINATING CEILING FAN

See the full line of Kichler®
Ceiling Fans in catalog K416
or visit kichler.com.

B | 300181 OZ



C | 42382 MIZ
Chandelier



D | 42383 MIZ
Chandelier

LACEY™

	ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/ STEM	NOTES
A	42381	MIZ	(5) 60W (C)	25	25.75	100	28	72	Additional chain 2996 MIZ.
B	300181	OZ	---	---	---	---	---	---	See the full line of Kichler® Ceiling Fans in catalog K416 or visit kichler.com .
C	42382	MIZ	(9) 60W (C)	34.25	29.5	104	65	72	Additional chain 4901 MIZ.
D	42383	MIZ	(12) 60W (C)	42	32	106	65	72	Additional chain 4901 MIZ.

Measurements shown in inches. U.S. & Canada Patent Pending.

MATCHING BATH

See matching bath fixtures on page 447.



E | 45281 MIZ
Wall Sconce



F | 42384 MIZ
Mini Pendant

Satin Etched
White Glass



G | 42386 MIZ
Semi Flush



H | 42399 MIZ
Semi FLush



Satin Etched
White Glass

J | 42387 MIZ
Semi Flush



K | 42385 MIZ
Pendant

LACEY™

ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	STEM TILT	EXTRA WIRE	CHAIN/STEM	EXT.	HCWO	NOTES
E	MIZ	(1) 60W (C)	5	10.75	---	---	---	---	7	6.5	Ⓚ
F	MIZ	(1) 60W (C/K) Ⓚ	6	10.25	49	90°	54	---	---	---	Additional stem 2999 (12") MIZ. Krypton bulb included.
G	MIZ	(3) 100W (M)	15	10.75	---	---	---	---	---	---	Ⓜ (18-25W CFL)
H	MIZ	(5) 100W (M)	28	15.25	---	---	---	---	---	---	Ⓜ (23-30W CFL)
J	MIZ	(4) 100W (M)	20	13	---	---	---	---	---	---	Ⓜ (23-30W CFL)
K	MIZ	(4) 100W (M)	20	23.5	98	---	14	72	---	---	(23-30W CFL) Additional chain 2996 MIZ.

Measurements shown in inches. U.S. & Canada Patent Pending.

KENSINGTON™

OLDE BRONZE® FINISH



A | 43331 OZ
Chandelier



B | 43332 OZ
Foyer Pendant



C | 43334 OZ
Wall Sconce

Shown with Optional
Vintage Squirrel
Cage Filament Bulb
4071 CLR.



D | 43333 OZ
Mini Pendant



Shown with
Optional
Vintage Squirrel
Cage Filament
Bulb 5971 CLR.

E | 43330 OZ
Chandelier



VINTAGE FILAMENT BULB


SOLD SEPARATELY
40W Candelabra Base
5971 CLR



VINTAGE FILAMENT BULB

SOLD SEPARATELY
60W Medium Base
4071 CLR

KENSINGTON™

	ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/ STEM	EXT.	HCWO	NOTES
A	43331	OZ	(9) 60W (C)	33.75	32.75	107	40	72	---	---	Additional chain 2996 OZ.
B	43332	OZ	(4) 60W (C)	16.25	27	68	50	36	---	---	Additional chain 2996 OZ, additional stem 2999 (12") OZ. Sloped ceiling kit included.
C	43334	OZ	(1) 60W (C)	5.25	13.5	---	---	---	7.5	9.25	D
D	43333	OZ	(1) 60W (M)	8.25	16.25	57	68	36	---	---	 (23-30W CFL) Additional chain 2996 OZ, additional stem 2999 (12") OZ. Sloped ceiling kit included.
E	43330	OZ	(5) 60W (C)	25	27.25	102	15	72	---	---	Additional chain 2996 OZ.

Measurements shown in inches. U.S. & Canada Patent Pending.

MONROE™

STERLING GOLD™ FINISH WITH
SATIN ETCHED GLASS



A | 43192 SGD
Grand Chandelier



B | 43159 SGD
Chandelier

MONROE™

	ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/STEM	NOTES
A	43192	SGD	(16) 75W (M)	45	48	122	29	72	① (18-25W CFL) Additional chain 4908 SGD.
B	43159	SGD	(9) 100W (M)	33.5	37.75	112	34	72	② (23-30W CFL) Additional chain 4901 SGD.
C	43155	SGD	(3) 100W (M)	23	29.5	104	35	72	③ (23-30W CFL) Additional chain 2996 SGD.
D	43158	SGD	(5) 100W (M)	27	25	99	20	72	④ (23-30W CFL) Additional chain 2996 SGD.
E	43156	SGD	(5) 100W (M)	27.5	29.5	104	35	72	⑤ (23-30W CFL) Additional chain 2996 SGD.
F	43167	SGD	(8) 60W (C)	27	44.75	119	34	72	Additional chain 2996 SGD.

Measurements shown in inches.



C | 43155 SGD
Chandelier



D | 43158 SGD
Chandelier



E | 43156 SGD
Chandelier



F | 43167 SGD
Foyer Chandelier

MONROE™

STERLING GOLD™ FINISH WITH
SATIN ETCHED GLASS



A | 43165 SGD
Foyer Pendant



B | 43164 SGD
Inverted Pendant



C | 43166 SGD
Foyer Chandelier



D | 43169 SGD
Semi Flush



E | 43170 SGD
Wall Sconce



F | 43163 SGD
Inverted Pendant



G | 43162 SGD
Mini Pendant

MONROE™

	ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	STEM TILT	EXTRA WIRE	CHAIN/STEM	EXT.	HCWO	NOTES
A	43165	SGD	(4) 60W (C)	15	27	101	---	34	72	---	---	Additional chain 2996 SGD.
B	43164	SGD	(3) 100W (M)	26.75	32.75	107	---	14	72	---	---	☑ (23-30W CFL) Additional chain 2996 SGD.
C	43166	SGD	(8) 60W (C)	23	40.75	115	---	34	72	---	---	Additional chain 2996 SGD.
D	43169	SGD	(2) 100W (M)	17.25	14.25	---	---	---	---	---	---	☑ (23-30W CFL)
E	43170	SGD	(1) 100W (M)	6	14	---	---	---	---	9.25	8	☑ (23-30W CFL) May be installed with glass up or down.
F	43163	SGD	(2) 100W (M)	17.5	24.75	99	---	20	72	---	---	☑ (23-30W CFL) Additional chain 2996 SGD.
G	43162	SGD	(1) 100W (M)	7	16	54	90°	60	36	---	---	☑ (23-30W CFL) Additional stem 2999 (12") SGD.

Measurements shown in inches.

MONROE™

BRUSHED NICKEL FINISH WITH SATIN ETCHED
GLASS OR OLDE BRONZE® FINISH WITH
LIGHT UMBER ETCHED GLASS



B | 43159 NI, OZ
Chandelier



A | 43192 NI, OZ
Grand Chandelier



C | 43155 NI, OZ
Chandelier



D | 43158 NI, OZ
Chandelier



E | 43156 NI, OZ
Chandelier



F | 43167 NI, OZ
Foyer Chandelier

MONROE™

	ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/STEM	NOTES
A	43192	NI, OZ	(16) 75W (M)	45	48	122	29	72	① (18-25W CFL) Additional chain 4908 NI, OZ.
B	43159	NI, OZ	(9) 100W (M)	33.5	37.75	112	34	72	② (23-30W CFL) Additional chain 4901 NI, OZ.
C	43155	NI, OZ	(3) 100W (M)	23	29.5	104	35	72	③ (23-30W CFL) Additional chain 2996 NI, OZ.
D	43158	NI, OZ	(5) 100W (M)	27	25	99	20	72	④ (23-30W CFL) Additional chain 2996 NI, OZ.
E	43156	NI, OZ	(5) 100W (M)	27.5	29.5	104	35	72	⑤ (23-30W CFL) Additional chain 2996 NI, OZ.
F	43167	NI, OZ	(8) 60W (C)	27	44.75	119	34	72	Additional chain 2996 NI, OZ.

Measurements shown in inches.



MONROE™

BRUSHED NICKEL FINISH WITH SATIN ETCHED
GLASS OR OLDE BRONZE® FINISH WITH
LIGHT UMBER ETCHED GLASS



A | 43165 NI, OZ
Foyer Pendant



B | 43164 NI, OZ
Inverted Pendant



C | 43166 NI, OZ
Foyer Chandelier

MATCHING BATH

See matching
bath fixtures
on pages 484-487.





D | 43169 NI, OZ
Semi Flush



E | 43170 NI, OZ
Wall Sconce



F | 43163 NI, OZ
Inverted Pendant



G | 43162 NI, OZ
Mini Pendant

MONROE™

	ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	STEM TILT	EXTRA WIRE	CHAIN/STEM	EXT.	HCWO	NOTES
A	43165	NI, OZ	(4) 60W (C)	15	27	101	---	34	72	---	---	Additional chain 2996 NI, OZ.
B	43164	NI, OZ	(3) 100W (M)	26.75	32.75	107	---	14	72	---	---	☑ (23-30W CFL) Additional chain 2996 NI, OZ.
C	43166	NI, OZ	(8) 60W (C)	23	40.75	115	---	34	72	---	---	Additional chain 2996 NI, OZ.
D	43169	NI, OZ	(2) 100W (M)	17.25	14.25	---	---	---	---	---	---	☑ (23-30W CFL)
E	43170	NI, OZ	(1) 100W (M)	6	14	---	---	---	---	9.25	8	☑ (23-30W CFL) May be installed with glass up or down.
F	43163	NI, OZ	(2) 100W (M)	17.5	24.75	99	---	20	72	---	---	☑ (23-30W CFL) Additional chain 2996 NI, OZ.
G	43162	NI, OZ	(1) 100W (M)	7	16	54	90°	60	36	---	---	☑ (23-30W CFL) Additional stem 2999 (12") NI, OZ.

Measurements shown in inches.



CAMERENA™

BRUSHED NICKEL FINISH WITH WHITE SCAVO
GLASS OR OLDE BRONZE® FINISH WITH WHITE
SCAVO GLASS WITH LIGHT UMBER INSIDE TINT



A | 43225 NI, OZ
Chandelier



B | 43224 NI, OZ
Chandelier



C | 43226 NI, OZ
Chandelier



D | 43234 NI, OZ
Grand Chandelier



E | 43232 NI, OZ
Semi Flush



F | 45421 NI, OZ
Wall Sconce

MATCHING BATH

See matching
bath fixtures
on page 482-483.



G | 43223 NI, OZ
Chandelier/Dinette



H | 43230 NI, OZ
Mini Pendant



J | 43227 NI, OZ
Inverted Pendant

CAMERENA™

	ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	STEM TILT	EXTRA WIRE	CHAIN/ STEM	EXT.	HCWO	NOTES
A	43225	NI, OZ	(5) 100W (M)	27	29	103	---	7	72	---	---	Ⓢ (23-30W CFL) Additional chain 2996 NI, OZ.
B	43224	NI, OZ	(5) 100W (M)	27	31.25	106	---	5	72	---	---	Ⓢ (23-30W CFL) Additional chain 2996 NI, OZ.
C	43226	NI, OZ	(9) 100W (M)	30	34.5	109	---	9	72	---	---	Ⓢ (23-30W CFL) Additional chain 2996 NI, OZ.
D	43234	NI, OZ	(16) 75W (M)	45	48.25	123	---	44	72	---	---	Ⓢ (18-25W CFL) Additional chain 4901 NI, OZ.
E	43232	NI, OZ	(3) 100W (M)	18	14.5	---	---	---	---	---	---	Ⓢ (23-30W CFL)
F	45421	NI, OZ	(1) 100W (M)	6	12.5	---	---	---	---	8.75	8.5	Ⓢ (23-30W CFL) May be installed with glass up or down.
G	43223	NI, OZ	(3) 100W (M)	20	24.5	99	---	11	72	---	---	Ⓢ (23-30W CFL) Additional chain 2996 NI, OZ.
H	43230	NI, OZ	(1) 100W (M)	7	16.5	55	90°	52	36	---	---	Ⓢ (23-30W CFL) Additional stem 2999 (12") NI, OZ.
J	43227	NI, OZ	(3) 100W (M)	18	21.5	96	---	14	72	---	---	Ⓢ (23-30W CFL) Additional chain 2996 NI, OZ.

Measurements shown in inches.

NI
Brushed Nickel

OZ
Olde Bronze®

SERINA

BLACK OR BRUSHED NICKEL FINISH WITH
SATIN ETCHED WHITE GLASS



A | 43631 BK, NI
Chandelier



B | 43630 BK, NI
Chandelier



C | 43632 BK, NI
Chandelier

MATCHING BATH

See matching
bath fixtures
on pages 508-509.





D | 45731 BK, NI
Wall Sconce



E | 43636 BK, NI
Semi Flush



F | 43634 BK, NI
Mini Pendant



G | 43635 BK, NI
Inverted Pendant

SERINA

	ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/STEM	EXT.	HCWO	NOTES
A	43631	BK, NI	(5) 100W (M)	24.75	21	95	34	72	---	---	☑ (18-25W CFL)
B	43630	BK, NI	(3) 100W (M)	19.5	19.5	94	34	72	---	---	☑ (18-25W CFL)
C	43632	BK, NI	(9) 100W (M)	30	29.75	104	70	72	---	---	☑ (18-25W CFL)
D	45731	BK, NI	(1) 100W (M)	5.5	9	---	---	---	6.25	5.75	☑ (18-25W CFL)
E	43636	BK, NI	(2) 60W (M) A19 ✦	12.75	8.5	---	---	---	---	---	☑ (13-15W CFL)
F	43634	BK, NI	(1) 100W (M)	5.5	6.75	45	67	36	---	---	☑ (18-25W CFL) Additional chain 2996 BK, NI, additional stem 2999 (12") BK, NI and/or additional stem 2997 (24") NI. Sloped ceiling kit included.
G	43635	BK, NI	(3) 100W (M)	17	23.5	98	20	72	---	---	☑ (23-30W CFL)

Measurements shown in inches. U.S. & Canada Patent Pending.

BK
Black

NI
Brushed Nickel

GRANBY™

BRUSHED PEWTER OR OLDE BRONZE® FINISH WITH
SATIN ETCHED CASED OPAL GLASS



A | 42556 BPT, OZ
Mini Chandelier



B | 42557 BPT, OZ
Chandelier



C | 42559 BPT, OZ
Chandelier

MATCHING BATH

See matching
bath fixtures
on page 469.





D | 42563 BPT, OZ
Semi Flush



E | 45358 BPT, OZ
Wall Sconce



F | 42561 BPT, OZ
Inverted Pendant



G | 42562 BPT, OZ
Mini Pendant

GRANBY™

	ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/STEM	EXT.	HCWO	NOTES
A	42556	BPT, OZ	(3) 100W (M)	19	16.5	55	74	36	---	---	Ⓜ (18-25W CFL) Additional chain 2996 BPT, OZ, additional stem 2999 (12") BPT, OZ. Sloped ceiling kit included.
B	42557	BPT, OZ	(5) 100W (M)	24	20.5	59	74	36	---	---	Ⓜ (18-25W CFL) Additional chain 2996 BPT, OZ, additional stem 2999 (12") BPT, OZ. Sloped ceiling kit included.
C	42559	BPT, OZ	(9) 100W (M)	33.25	32	70	110	36	---	---	Ⓜ (18-25W CFL) Additional chain 4901 BPT, OZ, additional stem 4935 (12") BPT, OZ. Sloped ceiling kit included.
D	42563	BPT, OZ	(3) 75W (M)	17.25	14	---	---	---	---	---	Ⓜ (18-25W CFL)
E	45358	BPT, OZ	(1) 100W (M)	5.75	14	---	---	---	7.5	7	Ⓜ (18-25W CFL) May be installed with glass up or down.
F	42561	BPT, OZ	(3) 100W (M)	24.5	24.5	63	92	36	---	---	Ⓜ (23-30W CFL) Additional chain 2996 BPT, OZ, additional stem 2999 (12") BPT, OZ. Sloped ceiling kit included.
G	42562	BPT, OZ	(1) 100W (M)	5.25	12.75	47	62	36	---	---	Ⓜ (18-25W CFL) Additional chain 2996 BPT, OZ, additional stem 2999 (12") BPT, OZ. Height includes one 6" stem. Sloped ceiling kit included.

Measurements shown in inches. U.S. & Canada Patent Pending.

BPT
Brushed Pewter

OZ
Olde Bronze®

LANGFORD™

BRUSHED NICKEL OR
OLDE BRONZE® FINISH WITH
SATIN ETCHED WHITE GLASS



Shown as
Inverted Pendant - 15.25" H.

CONVERTIBLE

Create two distinct lighting
options with one fixture:
Inverted Pendant or Semi Flush.

A | 3694 NI, OZ



Shown as
Semi Flush - 13.25" H.



B | 1784 NI, OZ
Chandelier



C | 1781 NI, OZ
Chandelier/Dinette



D | 1789 NI, OZ
Chandelier

LANGFORD™

ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/STEM	NOTES
A	3694 NI, OZ	(2) 100W (M)	15	15.25	90	30	72	(23-30W CFL) Additional chain 2996 NI, OZ.
B	1784 NI, OZ	(9) 100W (M)	33	30.5	105	54	72	(9-13W CFL) Additional chain 2996 NI, OZ.
C	1781 NI, OZ	(3) 100W (M)	22	17.25	92	25	72	(9-13W CFL) Additional chain 2996 NI, OZ.
D	1789 NI, OZ	(15) 75W (M)	42	43	117	42	72	(9-13W CFL) Additional chain 2996 NI, OZ.

Measurements shown in inches.



E | 8044 NI, OZ
Flush Mount



F | 3482 NI, OZ
Mini Pendant



G | 5388 NI, OZ
Wall Sconce



Shown as
Inverted Pendant - 15.25" H.

CONVERTIBLE

Create two distinct lighting
options with one fixture:
Inverted Pendant or Semi Flush.

H | 3681 NI, OZ



Shown as
Semi Flush - 13.25" H.



J | 1788 NI, OZ
Mini Chandelier



K | 1783 NI, OZ
Chandelier



L | 3384 NI, OZ
Inverted Pendant

MATCHING BATH

See matching
bath fixtures
on page 510-511.



LANGFORD™

ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	STEM TILT	EXTRA WIRE	CHAIN/STEM	EXT.	HCWO	NOTES
E	8044 NI, OZ	(2) 75W (M)	13	6	---	---	---	---	---	---	
F	3482 NI, OZ	(1) 100W (M)	7	7.75	47	90°	68	36	---	---	(18-25W CFL) Additional chain 2996 NI, OZ, additional stem 2999 (12") NI, OZ and/or 2997 (24") NI. Sloped ceiling kit included.
G	5388 NI, OZ	(1) 100W (M)	7.25	8	---	---	---	---	8.25	4.5	(9-13W CFL) May be installed with glass up or down.
H	3681 NI, OZ	(2) 100W (M)	18.75	15.25	54	---	6	36	---	---	(13-15W CFL) Additional chain 2996 NI, OZ.
J	1788 NI, OZ	(5) 100W (M)	16.5	17.25	92	---	24	72	---	---	(9-13W CFL) Additional chain 2996 NI, OZ.
K	1783 NI, OZ	(5) 100W (M)	27.25	24.5	99	---	17	72	---	---	(9-13W CFL) Additional chain 2996 NI, OZ.
L	3384 NI, OZ	(3) 100W (M)	22	25.5	100	---	20	72	---	---	(9-13W CFL) Additional chain 2996 NI, OZ.

Measurements shown in inches.

NI
Brushed Nickel

OZ
Olde Bronze®

OLYMPIA™

OLDE BRONZE® FINISH WITH
SUNSET MARBLE GLASS



A | 3606 OZ
Semi Flush



B | 3278 OZ
Inverted Pendant



C | 3279 OZ
Inverted Pendant

COORDINATING CEILING FAN

See the full line of Kichler®
Ceiling Fans in catalog K416
or visit kichler.com.

D | 300011 OZ



OLYMPIA™

ITEM #	FINISH	INCAND. BULB	W	H	OVRLL. H	EXTRA WIRE	CHAIN/STEM	NOTES
A	3606 OZ	(3) 100W (M)	24	11.25	---	---	---	☑ (23-30W CFL)
B	3278 OZ	(3) 150W (M) A21	24	21	59	59	39	☑ (23-30W CFL) Add. stem 2999 (12") OZ.
C	3279 OZ	(5) 150W (M)	36	31	69	81	36	☑ (23-30W CFL) Add. chain 4901 OZ, add. stem 2999 (12") OZ. Sloped ceiling kit included
D	300011 OZ	(6) 15W (C)	60	---	---	78	---	See the full line of Kichler® Ceiling Fans in catalog K416 or visit kichler.com .

Measurements shown in inches. U.S. & Canada Patent Pending.

OLYMPIA™

ANTIQUE PEWTER FINISH WITH
SATIN ETCHED WHITE GLASS



A | 3278 AP
Inverted Pendant



B | 3606 AP
Semi Flush



C | 3279 AP
Inverted Pendant

COORDINATING CEILING FAN

See the full line of Kichler®
Ceiling Fans in catalog K416
or visit kichler.com.

D | 300011 AP



OLYMPIA™

ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	STEM TILT	EXTRA WIRE	CHAIN/STEM	NOTES	
A	3278	AP	(3) 150W (M)	24	21	59	45°(12:12)	59	36	☑ (23-30W CFL) Add. stem 2999 (12") AP.
B	3606	AP	(3) 100W (M)	24	11.25	---	---	---	---	☑ (23-30W CFL)
C	3279	AP	(5) 150W (M)	36	31	69	---	81	36	☑ (23-30W CFL) Add. chain 4901 AP, add. stem 2999 (12") AP. Sloped ceiling kit included.
D	300011	AP	(6) 15W (C)	60	---	---	---	78	---	See the full line of Kichler® Ceiling Fans in catalog K416 or visit kichler.com .

Measurements shown in inches. U.S. Design Patent No. D577,850.

AUBREY

BRUSHED NICKEL OR OLDE BRONZE® FINISH
WITH SATIN ETCHED CASED OPAL GLASS



A | 45568 NI, OZ
Wall Sconce



B | 43667 NI, OZ
Inverted Pendant



C | 43666 NI, OZ
Chandelier

MATCHING BATH

See matching bath fixtures on pages 497-498.



AUBREY

ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/STEM	EXT.	HCWO	NOTES
A	45568	NI, OZ	(1) 100W (M)	5.5	10.75	---	---	7.25	5.5	Ⓛ (23-30W CFL) May be installed with glass up or down.
B	43667	NI, OZ	(3) 100W (M)	17.5	16.25	55	63	36	---	Ⓛ (23-30W CFL) Additional chain 2996 NI, OZ, additional stem 2999 (12") NI, OZ and/or 2997 (24") NI. Sloped ceiling kit included.
C	43666	NI, OZ	(9) 100W (M)	28.75	31.25	70	84	36	---	Ⓛ (23-30W CFL) Additional chain 2996 NI, OZ, additional stem 2999 (12") NI, OZ and/or 2997 (24") NI. Sloped ceiling kit included.

Measurements shown in inches. U.S. & Canada Patent Pending.



D | 43668 NI, OZ
Mini Pendant



E | 43669 NI, OZ
Semi Flush



F | 43664 NI, OZ
Chandelier



G | 43665 NI, OZ
Chandelier

AUBREY

	ITEM #	FINISH	INCAND. BULB	W	H	OVRLL. H	EXTRA WIRE	CHAIN/STEM	NOTES
D	43668	NI, OZ	(1) 100W (M)	4.75	12.75	51	63	36	(23-30W CFL) Additional chain 2996 NI, OZ, additional stem 2999 (12") NI, OZ and/or 2997 (24") NI. Sloped ceiling kit included.
E	43669	NI, OZ	(3) 100W (M)	15	13	---	---	---	(23-30W CFL)
F	43664	NI, OZ	(3) 100W (M)	21.5	19.25	58	60	36	(23-30W CFL) Additional chain 2996 NI, OZ, additional stem 2999 (12") NI, OZ and/or 2997 (24") NI. Sloped ceiling kit included.
G	43665	NI, OZ	(5) 100W (M)	25	23	61	57	36	(23-30W CFL) Additional chain 2996 NI, OZ, additional stem 2999 (12") NI, OZ and/or 2997 (24") NI. Sloped ceiling kit included.

Measurements shown in inches. U.S. & Canada Patent Pending.

NI
Brushed Nickel

OZ
Olde Bronze®

KEIRAN

BRUSHED NICKEL OR OLDE BRONZE® FINISH
WITH SATIN ETCHED WHITE GLASS



A | 43512 NI, OZ
Semi Flush



B | 43509 NI, OZ
Foyer Pendant



C | 43506 NI, OZ
Chandelier

MATCHING BATH

See matching bath fixtures on pages 506-507.



KEIRAN

	ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/STEM	NOTES
A	43512	NI, OZ	(2) 75W (M)	15	13	---	---	---	☑ (18-25W CFL)
B	43509	NI, OZ	(1) 100W (M)	10.5	24.75	99	20	72	☑ (23-30W CFL) Additional chain 2996 NI, OZ.
C	43506	NI, OZ	(9) 100W (M)	29	33.25	108	19	72	☑ (23-30W CFL) Additional chain 2996 NI, OZ.

Measurements shown in inches. U.S. & Canada Patent Pending.



D | 45504 NI, OZ
Wall Sconce



E | 43511 NI, OZ
Mini Pendant



F | 43503 NI, OZ
Chandelier



G | 43504 NI, OZ
Chandelier

KEIRAN

	ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	STEM TILT	EXTRA WIRE	CHAIN/STEM	EXT.	HCWO	NOTES
D	45504	NI, OZ	(1) 100W (M)	6	8.5	---	---	---	---	9.25	3.25	(23-30W CFL) May be installed with glass up or down.
E	43511	NI, OZ	(1) 100W (M)	6	6.75	45	90°	68	36	---	---	(23-30W CFL) Additional stem 2999 (12") NI, OZ and/or 2997 (24") NI.
F	43503	NI, OZ	(3) 100W (M)	20.75	20	94	---	21	72	---	---	(23-30W CFL) Additional chain 2996 NI, OZ.
G	43504	NI, OZ	(5) 100W (M)	24.5	23.25	98	---	18	72	---	---	(23-30W CFL) Additional chain 2996 NI, OZ.

Measurements shown in inches. U.S. & Canada Patent Pending.



ARMIDA™

BRUSHED NICKEL OR OLDE BRONZE® FINISH WITH
SATIN ETCHED WHITE GLASS



A | 43074 NI, OZ
Chandelier



B | 43073 NI, OZ
Mini Chandelier



C | 43075 NI, OZ
Chandelier

MATCHING BATH

See matching
bath fixtures
on pages 515-517.





D | 43076 NI, OZ
Foyer Pendant



E | 43077 NI, OZ
43077 NIFL
Mini Pendant



F | 45374 NI, OZ
Wall Sconce

CONVERTIBLE

Create two distinct lighting options with one fixture:
Inverted Pendant or Semi Flush.



Shown as
Inverted Pendant - 15.25" H.



Shown as
Semi Flush - 13.75" H.

G | 3694 NIW, OZW

ARMIDA™

ITEM #	FLUOR. ITEM#	FINISH	INCAND. BULB	FLUOR. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/STEM	EXT.	HCWO	NOTES
A	43074	NI, OZ	(5) 100W (M)	---	25.25	18	56	62	36	---	---	Ⓜ (23-30W CFL) Additional chain 2996 NI, OZ.
B	43073	NI, OZ	(3) 100W (M)	---	18	14.25	53	65	36	---	---	Ⓜ (23-30W CFL) Additional chain 2996 NI, OZ.
C	43075	NI, OZ	(9) 100W (M)	---	32.5	26.5	65	56	36	---	---	Ⓜ (23-30W CFL) Additional chain 2996 NI, OZ.
D	43076	NI, OZ	(1) 100W (M)	---	12.75	24.25	63	64	36	---	---	Ⓜ (23-30W CFL) Additional chain 2996 NI, OZ.
E	43077	43077 NIFL	(1) 100W (M)	(1) 13W (GU24) Ⓜ Ⓜ Ⓜ	4.75	8	47	68	36	---	---	Ⓜ (23-30W CFL) Additional chain 2996 NI, OZ, add. stem 2999 (12") NI, OZ and/or 2997 (24") NI. Sloped ceiling kit included.
F	45374	NI, OZ	(1) 100W (M)	---	5	10.75	---	---	---	7.25	7	Ⓜ (23-30W CFL) May be installed with glass up or down.
G	3694	---	(2) 100W (M)	---	15	15.25	90	30	72	---	---	Ⓜ (23-30W CFL) Additional chain 2996 NI, OZ.

Measurements shown in inches. U.S. & Canada Patent Pending.

NI
Brushed Nickel

OZ
Olde Bronze®

WEDGEPORT™ & WEDGEPORT™ ENERGY EFFICIENT

BRUSHED NICKEL FINISH WITH SATIN ETCHED GLASS OR
OLDE BRONZE® FINISH WITH UMBER ETCHED GLASS



A | 2084 NI, OZ
Chandelier/Dinette



B | 3585 NI, OZ
10742 NI, OZ
Inverted Pendant



C | 2086 NI, OZ
10741 NI, OZ
Chandelier

WEDGEPORT™ & WEDGEPORT™ ENERGY EFFICIENT

ITEM #	FLUOR. ITEM #	FINISH	INCAND. BULB	FLUOR. BULB	W	H	OVRLL. H	EXTRA WIRE	CHAIN/STEM	NOTES
A	2084	---	NI, OZ (5) 100W (M)	---	21.5	19.75	94	20	72	☑ (18-25W CFL) Additional chain 2996 NI, OZ, additional stem 2999 (12") NI, OZ and/or 2997 (24") NI. Height includes one 6" stem. Sloped ceiling kit included.
B	3585	---	NI, OZ (2) 150W (M)	---	19.25	20.75	95	19	72	Additional chain 2996 NI, OZ.
B	---	10742	NI, OZ	(2) 13W (GU24) Ⓡ Ⓢ	19.25	20.75	95	19	72	Additional chain 2996 NI, OZ.
C	2086	---	NI, OZ (9) 100W (M)	---	32	28	102	54	72	☑ (18-25W CFL) Additional chain 2996 NI, OZ.
C	---	10741	NI, OZ	(9) 13W (GU24) Ⓡ Ⓢ	32	28	102	48	72	Additional chain 2996 NI, OZ.

Measurements shown in inches.



D | 5284 NI, OZ
10636 NI, OZ
Wall Sconce



E | 6086 NI, OZ
Wall Sconce

MATCHING BATH

See matching
bath fixtures
on page 522.



F | 3584 NI, OZ
10743 NI, OZ
Mini Pendant



G | 3587 NI, OZ
Pendant



H | 2085 NI, OZ
10740 NI, OZ
Chandelier

WEDGEPORT™ & WEDGEPORT™ ENERGY EFFICIENT

ITEM #	FLUOR. ITEM #	FINISH	INCAND. BULB	FLUOR. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/STEM	EXT.	HCWO	NOTES
D	5284	NI, OZ	(1) 100W (M)	---	6.25	7.25	---	---	---	8	4.5	Ⓛ (18-25W CFL) May be installed with glass up or down.
D	---	10636	---	(1) 13W (GU24) Ⓛ Ⓡ	6.25	8	---	---	---	8	4.5	Ⓛ May be installed with glass up or down.
E	6086	NI, OZ	(1) 75W (M) ✓	---	8.5	8.25	---	---	---	4.25	3.5	Ⓛ (18-25W CFL) May be installed with glass up or down.
F	3584	NI, OZ	(1) 100W (M)	---	6.25	13	45	68	36	---	---	Ⓛ (18-25W CFL) Additional chain 2996 NI, OZ, additional stem 2999 (12") NI, OZ and/or 2997 (24") NI. Height includes one 6" stem. Sloped ceiling kit included.
F	---	10743	---	(1) 13W (GU24) Ⓛ Ⓡ	6.25	13.75	46	67	36	---	---	Additional chain 2996 NI, OZ, additional stem 2999 (12") NI, OZ and/or 2997 (24") NI. Height includes one 6" stem. Sloped ceiling kit included.
G	3587	NI, OZ	(1) 150W (M)	---	14	15.75	54	60	36	---	---	Additional chain 2996 NI, OZ, additional stem 2999 (12") NI, OZ and/or 2997 (24") NI. G-Type lamp recommended. Sloped ceiling kit included.
H	2085	NI, OZ	(5) 100W (M)	---	21.5	17.5	92	17	72	---	---	Ⓛ (18-25W CFL) Additional chain 2996 NI, OZ.
H	---	10740	---	(5) 13W (GU24) Ⓛ Ⓡ	23.5	17.5	92	23	72	---	---	Additional chain 2996 NI, OZ.

Measurements shown in inches.

NI
Brushed Nickel

OZ
Olde Bronze®

LILAH

ANTIQUE PEWTER OR OLDE BRONZE® FINISH
WITH SATIN ETCHED WHITE GLASS



A | 45550 AP, OZ
Wall Sconce



B | 43655 AP, OZ
Semi Flush



C | 43651 AP, OZ
Chandelier



D | 43652 AP, OZ
Chandelier

LILAH

ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/STEM	EXT.	HCWO	NOTES
A	AP, OZ	(1) 100W (M)	5	10	---	---	---	6.25	4.75	Ⓛ (23-30W CFL) May be installed with glass up or down.
B	AP, OZ	(3) 100W (M)	14	12.5	---	---	---	---	---	Ⓛ (23-30W CFL)
C	AP, OZ	(5) 100W (M)	24	24.75	99	16	72	---	---	Ⓛ (23-30W CFL) Additional chain 2996 AP, OZ.
D	AP, OZ	(9) 100W (M)	30	37.25	112	51	72	---	---	Ⓛ (23-30W CFL) Additional chain 2996 AP, OZ.

Measurements shown in inches.



E | 43654 AP, OZ
Mini Pendant



F | 43653 AP, OZ
Inverted Pendant



G | 43656 AP, OZ
Foyer Pendant



H | 43657 AP, OZ
Foyer Chandelier

MATCHING BATH

See matching
bath fixtures
on pages 501-502.



LILAH

	ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/ STEM	NOTES
E	43654	AP, OZ	(1) 100W (M)	4	13	87	27	72	(23-30W CFL) Additional chain 2996 AP, OZ.
F	43653	AP, OZ	(3) 100W (M)	17	23	97	22	72	(23-30W CFL) Additional chain 2996 AP, OZ.
G	43656	AP, OZ	(3) 100W (M)	14	26	100	16	72	(23-30W CFL) Additional chain 2996 AP, OZ.
H	43657	AP, OZ	(4) 100W (M)	17	33.5	108	11	72	(23-30W CFL) Additional chain 2996 AP, OZ.

Measurements shown in inches.

AP
Antique Pewter

OZ
Olde Bronze®

JOLIE

BRUSHED NICKEL OR OLDE BRONZE® FINISH
WITH SATIN ETCHED GLASS



B | 43638 NI, OZ
Chandelier



A | 43639 NI, OZ
Chandelier

MATCHING BATH

See matching
bath fixtures
on pages 513-514.



JOLIE

	ITEM #	FINISH	INCAND. BULB	W	H	OVRLL. H	EXTRA WIRE	CHAIN/ STEM	NOTES
A	43639	NI, OZ	(9) 100W (M)	28	28	66	39	36	☑ (23-30W CFL) Additional chain 2996 NI, OZ.
B	43638	NI, OZ	(5) 100W (M)	22	18.5	57	39	36	☑ (23-30W CFL) Additional chain 2996 NI, OZ.

Measurements shown in inches.



C | 45637 NI, OZ
Wall Sconce



D | 43640 NI, OZ
Mini Pendant



E | 43637 NI, OZ
Mini Chandelier

CONVERTIBLE

Create two distinct lighting options with one fixture:
Semi Flush or Inverted Pendant.

F | 43641 NI, OZ



Shown as
Semi Flush - 12" H.



Shown as
Inverted Pendant - 13.75" H.

JOLIE

ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/STEM	EXT.	HCWO	NOTES
C	45637 NI, OZ	(1) 100W (M)	5	9	---	---	---	6.25	4.25	Ⓛ (23-30W CFL) May be installed with glass up or down.
D	43640 NI, OZ	(1) 100W (M)	4.75	12.5	51	40	36	---	---	Ⓛ (23-30W CFL) Additional chain 2996 NI, OZ.
E	43637 NI, OZ	(3) 100W (M)	18	18	56	39	36	---	---	Ⓛ (23-30W CFL) Additional chain 2996 NI, OZ.
F	43641 NI, OZ	(2) 100W (M)	15	13.75	52	36	36	---	---	Ⓛ (23-30W CFL) Additional chain 2996 NI, OZ.

Measurements shown in inches.



NICHOLSON™

BRUSHED NICKEL OR OLDE BRONZE® FINISH
WITH SATIN ETCHED GLASS



A | 42882 NI, OZ
Small Foyer Pendant



B | 42881 NI, OZ
Pendant



C | 42884 NI, OZ
Chandelier



D | 42885 NI, OZ
Chandelier

NICHOLSON™

ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/STEM	NOTES	
A	42882	NI, OZ	(1) 150W (M)	13	21.25	96	30	72	☑ (30-52W CFL) Additional chain 2996 NI, OZ.
B	42881	NI, OZ	(1) 150W (M)	16	9.5	84	37	72	☑ (30-52W CFL) Additional chain 2996 NI, OZ. G Type bulb recommended.
C	42884	NI, OZ	(5) 100W (M)	25	21	95	36	72	☑ (18-25W CFL) Additional chain 2996 NI, OZ.
D	42885	NI, OZ	(9) 100W (M)	34	32	106	66	72	☑ (18-25W CFL) Additional chain 2996 NI, OZ.

Measurements shown in inches.



E | 45881 NI, OZ
Wall Sconce



F | 42880 NI, OZ
Mini Pendant



G | 42879 NI, OZ
Semi Flush



H | 42883 NI, OZ
Chandelier/Dinette

MATCHING BATH

See matching
bath fixtures
on pages 520-521.



NICHOLSON™

ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/STEM	EXT.	HCWO	NOTES
E	45881 NI, OZ	(1) 100W (M)	6	10	---	---	---	8.5	5	Ⓢ (18-25W CFL) May be installed with glass up or down.
F	42880 NI, OZ	(1) 100W (M)	6	8	82	25	72	---	---	Ⓢ (18-25W CFL) Additional chain 2996 NI, OZ.
G	42879 NI, OZ	(3) 100W (M)	16	13.25	---	---	---	---	---	Ⓢ (18-25W CFL)
H	42883 NI, OZ	(3) 100W (M)	21	21	95	30	72	---	---	Ⓢ (18-25W CFL) Additional chain 2996 NI, OZ.

Measurements shown in inches.



TELFORD™

BRUSHED NICKEL FINISH WITH ALABASTER SWIRL
GLASS OR OLDE BRONZE® FINISH WITH
UMBER ETCHED GLASS



A | 2076 NI, OZ
Chandelier



B | 2077 NI, OZ
Chandelier

MATCHING BATH

See matching
bath fixtures
on page 518-519.



TELFORD™

	ITEM #	FINISH	INCAND. BULB	W	H	OVRLL. H	EXTRA WIRE	CHAIN/ STEM	NOTES
A	2076	NI, OZ	(5) 100W (M)	24	17	91	27	72	Add. chain 2996 NI, OZ. May be installed with glass up or down.
B	2077	NI, OZ	(9) 100W (M)	33.5	25	99	63	72	Add. chain 2996 NI, OZ.

Measurements shown in inches.



C | 5991 NI, OZ
10604 NI
Wall Sconce



D | 8076 NI, OZ
Flush Mount








E | 3476 NI, OZ
Mini Pendant



F | 3277 NI, OZ
Inverted Pendant

TELFORD™

ITEM #	FLUOR. ITEM #	FINISH	INCAND. BULB	FLUOR. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/STEM	EXT.	HCWO	NOTES
C	5991	NI, OZ	(1) 100W (M)	---	7.25	12	---	---	---	9	6	Ⓧ May be installed with glass up or down.
C	---	10604 NI	---	(1) 13W (GU24)   	7.5	12	---	---	---	9	6	Ⓧ May be installed with glass up or down.
D	8076	NI, OZ	(2) 75W (M) 	---	14	7	---	---	---	---	---	
E	3476	NI, OZ	(1) 100W (M)	---	7.25	12.75	45	67	36	---	---	Add. chain 2996 NI, OZ, add. stem 2999 (12") NI, OZ and/or stem 2997 (24") NI. Height including one 6" stem. Sloped ceiling kit incl.
F	3277	NI, OZ	(3) 100W (M)	---	17.5	21.5	96	26	72	---	---	 (9-13W CFL) Add. chain 2996 NI, OZ.

Measurements shown in inches.



ANSONIA™

BRUSHED NICKEL FINISH WITH
SATIN ETCHED GLASS



A | 1748 NI
Chandelier/Dinette



B | 3349 NI
Pendant

MATCHING BATH

See matching
bath fixtures
on page 524.





C | 3345 NI
Mini Pendant



D | 5446 NI
Wall Sconce



ANSONIA™

	ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/STEM	EXT.	HCWO	NOTES
A	1748	NI	(5) 100W (M)	22	16.25	91	31	72	---	---	☑ (9-13W CFL) Additional chain 2996 NI. May be installed with glass up or down.
B	3349	NI	(1) 150W (M)	15	15	89	32	72	---	---	☑ (23-30W CFL) Additional chain 2996 NI. G Type bulb recommended.
C	3345	NI	(1) 100W (M)	4.75	13.75	88	25	72	---	---	☑ (9-13W CFL) Additional chain 2996 NI.
D	5446	NI	(1) 100W (M)	5.5	9.25	---	---	---	5.5	6.5	☑ (9-13W CFL) May be installed with glass up or down.
E	3348	NI	(1) 100W (M)	12	15.5	90	32	72	---	---	☑ (18-25W CFL) Additional chain 2996 NI.

Measurements shown in inches.

DOVER™

ANTIQUE BRASS, BRUSHED NICKEL, POLISHED BRASS, POLISHED CHROME, TANNERY BRONZE™ OR OLDE BRONZE® FINISH WITH ETCHED SEEDED OR ALABASTER SWIRL GLASS



A | 2020 AB, NI, TZ
Chandelier



B | 2021 NI, TZ
Chandelier



C | 2523 NI, TZ
Chandelier



D | 2520 NI, TZ
Chandelier

MATCHING BATH

See matching bath fixtures on page 523.



E | 6719 NI, TZ
Wall Sconce



F | 2019 NI, TZ
Mini Chandelier



CONVERTIBLE

Create two distinct lighting options with one fixture:
Inverted Pendant or Semi Flush.

H | 3502 NI, TZ



G | 2031 NI, TZ
Chandelier



Shown as
Inverted Pendant - 19" H.

DOVER™

ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/STEM	EXT.	HCWO	NOTES
A	2020 AB, NI, TZ	(5) 60W (C)	24	23	97	19	72	---	---	Additional chain 2996 AB, NI, TZ.
B	2021 NI, TZ	(5) 60W (C)	25.5	24.5	98.5	17	72	---	---	Additional chain 2996 NI, TZ.
C	2523 NI, TZ	(15) 60W (C)	36.5	45.5	119.5	80	72	---	---	Additional chain 4901 NI, TZ.
D	2520 NI, TZ	(9) 60W (C)	27.75	37	111	57	72	---	---	Additional chain 2996 NI, TZ.
E	6719 NI, TZ	(1) 100W (M)	6.25	6.5	---	---	---	6.75	4.25	Ⓢ May be installed with glass up or down.
F	2019 AB, NI, TZ	(4) 60W (C)	18	16	90	123	72	---	---	Additional chain 2996 AB, NI, TZ.
G	2031 NI, TZ	(9) 60W (C)	32.5	29	103	9	72	---	---	Additional chain 2996 NI, TZ.
H	3502 NI, TZ	(3) 100W (M)	17.75	19	93	21	72	---	---	Additional chain 2996 NI, TZ.

Measurements shown in inches.

AB
Antique Brass

NI
Brushed Nickel

TZ
Tannery Bronze™

DOVER™

ANTIQUE BRASS, BRUSHED NICKEL, POLISHED BRASS, POLISHED CHROME, STUCCO WHITE, TANNERY BRONZE™ OR OLDE BRONZE® FINISH WITH ETCHED SEEDED OR ALABASTER SWIRL GLASS



A | 2702 NI, OZ, TZ
Pendant



B | 2771 NI, TZ
Mini Pendant



COORDINATING CEILING FAN

See the full line of Kichler® Ceiling Fans in catalog K416 or visit kichler.com.

C | 300117 NI, TZ



D | 3623 NI, OZ, TZ
Semi Flush



E | 8065 NI, TZ
Flush Mount



F | 8655 CH, NI, PB, SC, TZ
Flush Mount



G | 8064 NI, TZ
Flush Mount



H | 8654 AB, CH, NI, SC, TZ
Flush Mount



J | 8653 CH, NI, SC, TZ
Flush Mount

DOVER™

ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/STEM	NOTES
A	NI, OZ, TZ	(1) 150W (M)	17.5	8.5	83	36	72	Ⓜ (9-13W CFL) Add. chain 2996 NI, OZ, TZ. G Type lamp rec.
B	NI, TZ	(1) 100W (M)	6.5	11.5	46	68	36	Add. chain 2996 NI, TZ, add. stem 2999 (12") NI, TZ and/or 2997 (24") NI. Height included one 6" stem. Sloped ceiling kit included.
C	NI, TZ	---	---	---	---	---	---	See the full line of Kichler® Ceiling Fans in catalog K416 or visit kichler.com .
D	NI, OZ, TZ	(3) 60W (M)	15.25	14	---	---	---	Ⓜ (13-15W CFL)
E	NI, TZ	(3) 60W (M) ❖	15.25	7.75	---	---	---	Ⓜ (13-15W CFL)
F	CH, NI, PB, SC, TZ	(3) 60W (M) ❖	15.25	6.25	---	---	---	Ⓜ (13-15W CFL) Satin Etched Glass.
G	NI, TZ	(2) 60W (M) ❖	13.25	6.25	---	---	---	Ⓜ (13-15W CFL)
H	AB, CH, NI, SC, TZ	(2) 60W (M) ❖	13.25	5.5	---	---	---	Ⓜ (13-15W CFL) Satin Etched Glass.
J	CH, NI, SC, TZ	(2) 60W (M) ❖	11.5	6	---	---	---	Ⓜ (13-15W CFL) Satin Etched Glass.

Measurements shown in inches.

WYNBERG™

BRUSHED NICKEL WITH ALABASTER SWIRL GLASS,
OLDE BRONZE® OR TANNERY BRONZE™ FINISH
WITH UMBER GLASS



A | 1770 NI, TZ
Mini Chandelier



B | 3293 NI, NIA, OZ, OZU
Chandelier/Dinette



C | 2022 NI, TZ
Chandelier



D | 2093 NI, OZ
Chandelier

CONVERTIBLE

Create two distinct lighting
options with one fixture:
Inverted Pendant or Semi Flush.



Shown as
Inverted Pendant - 15.25" H.



Shown as
Semi Flush - 13.5" H.

E | 3694 NI, OZ



F | 2693 NI, OZ
Mini Pendant



G | 2807 NI
Mini Pendant



H | 5294 NI, OZ
Wall Sconce

WYNBERG™

ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	STEM TILT	EXTRA WIRE	CHAIN/ STEM	EXT.	HCWO	NOTES
A	NI, TZ	(5) 60W (C)	17	12.75	87		25	72			Additional chain 2996 NI, TZ.
B	NI, NIA, OZ, OZU	(3) 100W (M)	21.75	13.25	88	---	64	72	---	---	Ⓜ (9-13W CFL) Add. chain 2996 NI, NIA, OZ, OZU.
C	NI, TZ	(5) 100W (M)	23	14	98	---	30	72	---	---	Add. chain 2996 NI, TZ. Satin Etched Seeded Glass.
D	NI, OZ	(5) 100W (M)	24.5	13.75	88	---	25	72	---	---	Ⓜ (23-30W CFL) Add. chain 2996 NI, OZ.
E	NI, OZ	(2) 100W (M)	15	15.25	90	---	30	72	---	---	Ⓜ (23-30W CFL) Add. chain 2996 NI, OZ.
F	NI, OZ	(1) 100W (M)	6	12	44	90°	64	36	---	---	Add. stem 2999 (12") NI, OZ, and/or add. stem 2997 (24") NI, OZ. Satin Etched Glass. Height includes one 6" stem.
G	NI	(1) 100W (M)	7	12.25	45	45°	68	---	---	---	Add. stem 2999 (12") NI and/or 2997 (24") NI. G Type lamp rec. Satin Etched Glass. Height includes one 6" stem.
H	NI, OZ	(1) 100W (M)	6	7.5	---	---	---	---	8.5	3.5	Ⓜ May be installed with glass up or down. Satin Etched Glass.

Measurements shown in inches.

AB
Antique Brass

CH
Polished Chrome

NI
Brushed Nickel

OZ
Olde Bronze®

PB
Polished Brass

SC
Stucco White

TZ
Tannery Bronze™

PENDANTS

CREATIVE & VERSATILE

When it comes to pendants, let your imagination – and your creativity – guide you. These great *anything goes* lights are designed for versatility and ingenuity. Cluster them above or around kitchen islands. Bring extra task lighting to a bathroom vanity or home office. Vary the height for visual interest or leave them level for a linear effect. Go eclectic and choose from multiple collections. Or place one alone above a seating area, nightstand or reading nook. Oh the possibilities!



City Loft™ Pendant 43784 PN | Page 336 & Pendant 43783 | Page 337



EVERLY™

BRUSHED NICKEL FINISH WITH
CLEAR SEEDED GLASS OR MERCURY GLASS



A | 42141 NICS
Clear Seeded Glass



B | 42046 NICS
Clear Seeded Glass



C | 42190 NI
Clear Seeded Glass

EVERLY™

	ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	STEM TILT	EXTRA WIRE	CHAIN/STEM	NOTES
A	42141	NICS	(1) 100W (M)	10.5	15.5	54	90°	56	36	Additional stem 2999 (12") NI and/or 2997 (24") NI. Glass is removable.
B	42046	NICS	(1) 100W (M)	13.75	20	60	90°	56	36	Additional stem 2999 (12") NI and/or 2997 (24") NI. Glass is removable.
C	42190	NI	(3) 100W (M)	16	22.75	61	---	62	36	Additional stem 2999 (12") NI and/or 2997 (24") NI. Glass is removable.

Measurements shown in inches. U.S. & Canada Patent Pending.



D | 42475 NIMER
Mercury Glass



E | 42044 NIMER
Mercury Glass



F | 42329 NICS
Clear Seeded Glass



G | 42328 NICS
Clear Seeded Glass



H | 42167 NIMER
Mercury Glass

EVERLY™

	ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	STEM TILT	EXTRA WIRE	CHAIN/STEM	NOTES
D	42475	NIMER	(1) 100W (M)	10.75	29.75	68	---	54	36	Ⓜ (9-11W CFL) Additional stem 2999 (12") NI and/or 2997 (24") NI. Glass is removable.
E	42044	NIMER	(1) 100W (M)	12	10.5	50	90°	56	36	Additional stem 2999 (12") NI and/or 2997 (24") NI. Glass is removable.
F	42329	NICS	(1) 100W (M)	19	16	54	90°	57	36	Additional stem 2999 (12") NI and/or 2997 (24") NI. Glass is removable.
G	42328	NICS	(1) 100W (M)	12.5	11.25	50	90°	59	36	Additional stem 2999 (12") NI and/or 2997 (24") NI. Glass is removable.
H	42167	NIMER	(1) 100W (M)	9.5	9.5	48	90°	59	36	Additional stem 2999 (12") NI and/or 2997 (24") NI. Glass is removable.

Measurements shown in inches. U.S. & Canada Patent Pending.

EVERLY™

POLISHED CHROME FINISH WITH
CLEAR GLASS



A | 42141 CHCLR
Clear Glass



B | 42046 CH
Clear Glass



C | 42198 CH
Clear Glass

EVERLY™

	ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	STEM TILT	EXTRA WIRE	CHAIN/STEM	NOTES
A	42141	CHCLR	(1) 100W (M)	10.5	15.5	54	90°	56	36	Additional stem 2999 (12") CH. Glass is removable.
B	42046	CH	(1) 100W (M)	13.75	20	60	90°	56	36	Additional stem 2999 (12") CH. Glass is removable.
C	42198	CH	(3) 100W (M)	20	27.5	66	---	60	36	Additional stem 2999 (12") CH. Glass is removable.

Measurements shown in inches. U.S. & Canada Patent Pending.



D | 42475 CHCLR
Clear Glass



E | 42456 CHCLR
Clear Glass



F | 42047 CH
Clear Glass



G | 42044 CH
Clear Glass

EVERLY™

	ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	STEM TILT	EXTRA WIRE	CHAIN/STEM	NOTES
D	42475	CHCLR	(1) 100W (M)	10.75	29.75	68	90°	54	36	Additional stem 2999 (12") CH. Glass is removable.
E	42456	CHCLR	(1) 100W (M)	7	14	52	90°	57	36	Additional stem 2999 (12") CH. Glass is removable.
F	42047	CH	(1) 100W (M)	8.75	18	58	90°	62	36	Additional stem 2999 (12") CH. Glass is removable.
G	42044	CH	(1) 60W (M)	12	10.5	50	90°	56	36	Additional stem 2999 (12") CH. Glass is removable.

Measurements shown in inches. U.S. & Canada Patent Pending.

EVERLY™

OLDE BRONZE® FINISH WITH
CLEAR SEEDED GLASS



A | 42328 OZCS
Clear Seeded Glass



B | 42329 OZCS
Clear Seeded Glass



C | 42141 OZCS
Clear Seeded Glass



D | 42046 OZCS
Clear Seeded Glass



E | 42190 OZ
Clear Seeded Glass

EVERLY™

ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	STEM TILT	EXTRA WIRE	CHAIN/STEM	NOTES	
A	42328	OZCS	(1) 100W (M)	12.5	11.5	50	90°	59	36	Additional stem 2999 (12") OZ. Glass is removable.
B	42329	OZCS	(1) 100W (M)	19	16	54	90°	57	36	Additional stem 2999 (12") OZ. Glass is removable.
C	42141	OZCS	(1) 100W (M)	10.5	15.75	54	90°	56	36	Additional stem 2999 (12") OZ. Glass is removable.
D	42046	OZCS	(1) 100W (M)	13.75	20	60	90°	56	36	Additional stem 2999 (12") OZ. Glass is removable.
E	42190	OZ	(3) 100W (M)	16	22.75	61	90°	62	36	Additional stem 2999 (12") OZ. Glass is removable.


Measurements shown in inches. U.S. & Canada Patent Pending.

EVERLY™


OLDE BRONZE® FINISH WITH
MERCURY OR CHAMPAGNE GLASS



A | 42475 OZMER
Mercury Glass



B | 42044 OZMER
Mercury Glass



C | 42167 OZMER
Mercury Glass



D | 42456 OZCP
Champagne Glass

EVERLY™

	ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	STEM TILT	EXTRA WIRE	CHAIN/STEM	NOTES
A	42475	OZMER	(1) 100W (M)	10.75	29.5	68	90°	54	36	Additional stem 2999 (12") OZ. Glass is removable.
B	42044	OZMER	(1) 100W (M)	12	10.5	50	90°	56	36	Additional stem 2999 (12") OZ. Glass is removable.
C	42167	OZMER	(1) 100W (M)	9.5	9.5	48	90°	59	36	Additional stem 2999 (12") OZ. Glass is removable.
D	42456	OZCP	(1) 100W (M)	7	14	52	90°	57	36	Additional stem 2999 (12") OZ. Glass is removable.

Measurements shown in inches. U.S. & Canada Patent Pending.

EVERLY™

OLDE BRONZE® FINISH WITH
CLEAR GLASS



A | 42141 OZCLR
Clear Glass



B | 42046 OZ
Clear Glass



C | 42198 OZ
Clear Glass

EVERLY™

	ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	STEM TILT	EXTRA WIRE	CHAIN/STEM	NOTES
A	42141	OZCLR	(1) 100W (M)	10.5	15.5	54	90°	56	36	Additional stem 2999 (12") OZ. Glass is removable.
B	42046	OZ	(1) 100W (M)	13.75	20	60	90°	56	36	Additional stem 2999 (12") OZ. Glass is removable.
C	42198	OZ	(3) 100W (M)	20	27.75	66	90°	60	36	Additional stem 2999 (12") OZ. Glass is removable.

Measurements shown in inches. U.S. & Canada Patent Pending.



D | 42475 OZCLR
Clear Glass



E | 42047 OZ
Clear Glass



F | 42456 OZCLR
Clear Glass



G | 42044 OZ
Clear Glass

EVERLY™

	ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	STEM TILT	EXTRA WIRE	CHAIN/STEM	NOTES
D	42475	OZCLR	(1) 100W (M)	10.75	29.75	68	90°	54	36	Additional stem 2999 (12") OZ. Glass is removable.
E	42047	OZ	(1) 100W (M)	8.75	18.25	58	90°	62	36	Additional stem 2999 (12") OZ. Glass is removable.
F	42456	OZCLR	(1) 100W (M)	7	14	52	90°	57	36	Additional stem 2999 (12") OZ. Glass is removable.
G	42044	OZ	(1) 60W (M)	12	10.5	50	90°	56	36	Additional stem 2999 (12") OZ. Glass is removable.

Measurements shown in inches. U.S. & Canada Patent Pending.

SILBERNE™

CLASSIC PEWTER OR NATURAL BRASS FINISH
WITH CLEAR SEEDED GLASS



A | 43739 CLP



A | 43739 NBR



B | 43738 CLP



B | 43738 NBR



C | 43737 CLP



C | 43737 NBR

SILBERNE™

	ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/STEM	NOTES
A	43739	CLP, NBR	(3) 100W (M)	18	13	52	70	36	Additional stem 2999 (12") CLP, NBR.
B	43738	CLP, NBR	(1) 100W (M)	10	10	48	65	36	Additional stem 2999 (12") CLP, NBR.
C	43737	CLP, NBR	(1) 100W (M)	13	13.25	52	70	36	Additional stem 2999 (12") CLP, NBR.

Measurements shown in inches. U.S. & Canada Patent Pending.

COBSON™

POLISHED NICKEL FINISH WITH ANTIQUE NICKEL ACCENTS



Shown as Pendant - 8" H.



Shown as Mini Pendant - 7.5" H.



Shown as Wall Sconce - 7.5" H.



Shown as Pendant - 7.5" H.



VINTAGE FILAMENT BULB

SOLD SEPARATELY
60W Medium Base
4071 CLR

CONVERTIBLE

Create two distinct lighting options with one fixture:
Pendant or Semi Flush.

A | 42585 PN



Shown as Semi Flush - 10.75" H.

PENDALETTE®

Create three distinct lighting options with one fixture:
Mini Pendant, Wall Sconce or Semi Flush.

B | 42579 PN



Shown as Semi Flush - 10" H.

CONVERTIBLE

Create two distinct lighting options with one fixture:
Pendant or Semi Flush.

C | 42580 PN



Shown as Semi Flush - 10" H.



D | 42649 PN
Pendant

COBSON™

	ITEM #	FINISH	INCAND. BULB	W	H	OVRLL. H	EXTRA WIRE	CHAIN/STEM	EXT.	HCWO	NOTES
A	42585	PN	(1) 100W (M)	16	8	46	66	36	---	---	☑ (23-30W CFL) Add. chain 2996 PN, add. stem 2999 (12") PN. Sloped ceiling kit included. Functioning on/off paddle switch.
B	42579	PN	(1) 100W (M)	8	7.5	46	66	36	10	2.5	☑ (23-30W CFL) Add. chain 2996 PN, add. stem 2999 (12") PN. Sloped ceiling kit included. Functioning on/off paddle switch.
C	42580	PN	(1) 100W (M)	12	7.5	46	66	36	---	---	☑ (23-30W CFL) Add. chain 2996 PN, add. stem 2999 (12") PN. Sloped ceiling kit included. Functioning on/off paddle switch.
D	42649	PN	(3) 100W (M)	20	9.5	48	62	36	---	---	☑ (23-30W CFL) Add. chain 2996 PN, add. stem 2999 (12") PN. Sloped ceiling kit included. Functioning on/off paddle switch.

Measurements shown in inches. U.S. & Canada Patent Pending.



COBSON™

NATURAL BRASS FINISH WITH ANTIQUE NICKEL ACCENTS



VINTAGE FILAMENT BULB

SOLD SEPARATELY
60W Medium Base
4071 CLR



Shown as
Pendant - 7.5" H.



Shown as
Wall Sconce - 7.5" H.



Shown as
Pendant - 8" H.



A | 42649 NBR
Pendant

CONVERTIBLE

Create two distinct lighting options with one fixture:
Pendant or Semi Flush.

B | 42580 NBR



Shown as
Semi Flush - 10" H.

PENDALETTE®

Create three distinct lighting options with one fixture:
Mini Pendant, Wall Sconce or Semi Flush.

C | 42579 NBR



Shown as
Semi Flush - 10" H.

CONVERTIBLE

Create two distinct lighting options with one fixture:
Pendant or Semi Flush.

D | 42585 NBR



Shown as
Semi Flush - 10.75" H.

COBSON™

	ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/STEM	EXT.	HCWO	NOTES
A	42649	NBR	(3) 100W (M)	20	9.5	48	62	36	---	---	☑ (23-30W CFL) Add. chain 2996 NBR, add. stem 2999 (12") NBR. Sloped ceiling kit included. Functioning on/off paddle switch.
B	42580	NBR	(1) 100W (M)	12	7.5	46	66	36	---	---	☑ (23-30W CFL) Add. chain 2996 NBR, add. stem 2999 (12") NBR. Sloped ceiling kit included. Functioning on/off paddle switch.
C	42579	NBR	(1) 100W (M)	8	7.5	46	66	36	10	2.5	☑ (23-30W CFL) Add. chain 2996 NBR, add. stem 2999 (12") NBR. Sloped ceiling kit included. Functioning on/off paddle switch.
D	42585	NBR	(1) 100W (M)	16	8	46	66	36	---	---	☑ (23-30W CFL) Add. chain 2996 NBR, add. stem 2999 (12") NBR. Sloped ceiling kit included. Functioning on/off paddle switch.

Measurements shown in inches. U.S. & Canada Patent Pending.

COBSON™

OLDE BRONZE® FINISH WITH ANTIQUE
NATURAL BRASS ACCENTS



Shown as
Pendant - 8" H.



Shown as
Mini Pendant - 7.5" H.



Shown as
Wall Sconce - 7.5" H.



Shown as
Pendant - 7.5" H.



VINTAGE
FILAMENT
BULB

SOLD SEPARATELY
60W Medium Base
4071 CLR

CONVERTIBLE

Create two distinct lighting
options with one fixture:
Pendant or Semi Flush.

A | 42585 OZ



Shown as
Semi Flush - 10.75" H.

PENDALETTE®

Create three distinct lighting
options with one fixture:
Mini Pendant, Wall Sconce or
Semi Flush.

B | 42579 OZ



Shown as
Semi Flush - 10" H.

CONVERTIBLE

Create two distinct lighting
options with one fixture:
Pendant or Semi Flush.

B | 42580 OZ



Shown as
Semi Flush - 10" H.



D | 42649 OZ
Pendant

COBSON™

	ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/STEM	EXT.	HCWO	NOTES
A	42585	OZ	(1) 100W (M)	16	8	46	66	36	---	---	(23-30W CFL) Add. chain 2996 OZ, add. stem 2999 (12") OZ. Sloped ceiling kit included. Functioning on/off paddle switch.
B	42579	OZ	(1) 100W (M)	8	7.5	46	66	36	10	2.5	(23-30W CFL) Add. chain 2996 OZ, add. stem 2999 (12") OZ. Sloped ceiling kit included. Functioning on/off paddle switch.
C	42580	OZ	(1) 100W (M)	12	7.5	46	66	36	---	---	(23-30W CFL) Add. chain 2996 OZ, add. stem 2999 (12") OZ. Sloped ceiling kit included. Functioning on/off paddle switch.
D	42649	OZ	(3) 100W (M)	20	9.5	48	62	36	---	---	(23-30W CFL) Add. chain 2996 OZ, add. stem 2999 (12") OZ. Sloped ceiling kit included. Functioning on/off paddle switch.

Measurements shown in inches. U.S. & Canada Patent Pending.

HATTERAS BAY™

POLISHED NICKEL FINISH WITH
CLEAR FRESNEL LENS

COORDINATING CEILING FAN

See the full line of Kichler®
Ceiling Fans in catalog K416
or visit kichler.com.

A | 300018 BSS



MATCHING FIXTURE

See matching Rail Lights
on page 377.



B | 2666 PN



C | 2664 PN



D | 2665 PN



E | 2682 PN



F | 2691 PN


HATTERAS BAY™

ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/ STEM	NOTES	
A	300018	BSS	---	---	---	---	---	See the full line of Kichler® Ceiling Fans in catalog K416 or visit kichler.com .	
B	2666	PN	(1) 150W (M)	13.25	11.5	50	71	36	☑ (18-25W CFL) Add. chain 2996 PN, add. stem 2999 (12") PN. Sloped ceiling kit included.
C	2664	PN	(1) 100W (M)	8	10.25	49	71	36	☑ (18-25W CFL) Add. chain 2996 PN, add. stem 2999 (12") PN. Sloped ceiling kit included.
D	2665	PN	(1) 100W (M)	11.75	10.25	49	71	36	☑ (18-25W CFL) Add. chain 2996 PN, add. stem 2999 (12") PN. Sloped ceiling kit included.
E	2682	PN	(1) 150W (M)	18	16	53	70	36	☑ (30-52W CFL) Add. chain 2996 PN, add. stem 4935 (12") PN. Sloped ceiling kit included. Clear Fresnel Lens.
F	2691	PN	(1) 200W (M)	23.75	19.5	58	67	36	☑ (52-65W CFL) Add. chain 4901 PN, add. stem 4935 (12") PN. Sloped ceiling kit included.

Measurements shown in inches.

HATTERAS BAY™

POLISHED NICKEL FINISH WITH SATIN ETCHED WHITE GLASS AND CLEAR FRESNEL LENS



A | 43764 PN



B | 43768 PN



C | 43767 PN



D | 43766 PN



E | 43765 PN

HATTERAS BAY™

ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/STEM	NOTES
A	PN	(1) 100W (M)	8	10.25	48	70	36	☑ (18-25W CFL) Add. chain 2996 PN, add. stem 2999 (12") PN. Sloped ceiling kit included.
B	PN	(1) 200W (M)	23.75	19.5	58	64	36	☑ (52-65W CFL) Add. chain 4901 PN, add. stem 4935 (12") PN. Sloped ceiling kit included.
C	PN	(1) 150W (M)	18	16.75	55	68	36	☑ (30-52W CFL) Add. chain 2996 PN, add. stem 4935 (12") PN. Sloped ceiling kit included. Clear Fresnel Lens.
D	PN	(1) 150W (M)	13	13.25	52	70	36	☑ (23-30W CFL) Add. chain 2996 PN, add. stem 2999 (12") PN. Sloped ceiling kit included.
E	PN	(1) 100W (M)	11.5	12	50	70	36	☑ (18-25W CFL) Add. chain 2996 PN, add. stem 2999 (12") PN. Sloped ceiling kit included.

Measurements shown in inches. U.S. & Canada Patent Pending.

HATTERAS BAY™

OLDE BRONZE® FINISH WITH
CLEAR FRESNEL LENS

MATCHING FIXTURE

See matching Rail Lights
on page 377.



MATCHING CEILING LIGHT

See matching Ceiling Lights
on page 380.



COORDINATING CEILING FAN

See the full line of Kichler®
Ceiling Fans in catalog K416
or visit kichler.com.

A | 300018 OBB



B | 2664 OZ



C | 2665 OZ



D | 2666 OZ



E | 2682 OZ



F | 2691 OZ

HATTERAS BAY™

ITEM #	FINISH	INCAND. BULB	W	H	OVRLL. H	EXTRA WIRE	CHAIN/ STEM	NOTES	
A	300018	OBB	---	---	---	---	---	See the full line of Kichler® Ceiling Fans in catalog K416 or visit kichler.com.	
B	2664	OZ	(1) 100W (M)	8	10.25	49	71	36	Ⓢ (18-25W CFL) Additional chain 2996 OZ, additional stem 2999 (12") OZ. Sloped ceiling kit incl.
C	2665	OZ	(1) 100W (M)	11.75	10.25	49	71	36	Ⓢ (18-25W CFL) Additional chain 2996 OZ, additional stem 2999 (12") OZ. Sloped ceiling kit incl.
D	2666	OZ	(1) 150W (M)	13.25	11.5	50	71	36	Ⓢ (18-25W CFL) Additional chain 2996 OZ, additional stem 2999 (12") OZ. Sloped ceiling kit incl.
E	2682	OZ	(1) 150W (M)	18	16	53	70	36	Ⓢ (30-52W CFL) Additional chain 2996 OZ, additional stem 4935 (12") OZ. Sloped ceiling kit incl. Clear Fresnel Lens.
F	2691	OZ	(1) 200W (M)	23.75	19.5	58	67	36	Ⓢ (52-65W CFL) Additional chain 4901 OZ, additional stem 4935 (12") OZ. Sloped ceiling kit incl.

Measurements shown in inches.

HATTERAS BAY™

OLDE BRONZE® FINISH
WITH SATIN ETCHED WHITE GLASS AND
CLEAR FRESNEL LENS



A | 43764 OZ



B | 43768 OZ



C | 43767 OZ



D | 43766 OZ



E | 43765 OZ

HATTERAS BAY™

	ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/STEM	NOTES
A	43764	OZ	(1) 100W (M)	8	10.25	48	70	36	Ⓢ (18-25W CFL) Add. chain 2996 OZ, add. stem 2999 (12") OZ. Sloped ceiling kit included.
B	43768	OZ	(1) 200W (M)	23.75	19.5	58	64	36	Ⓢ (52-65W CFL) Add. chain 4901 OZ, add. stem 4935 (12") OZ. Sloped ceiling kit included.
C	43767	OZ	(1) 150W (M)	18	16.75	55	68	36	Ⓢ (30-52W CFL) Add. chain 2996 OZ, add. stem 4935 (12") OZ. Sloped ceiling kit included. Clear Fresnel Lens.
D	43766	OZ	(1) 150W (M)	13	13.25	52	70	36	Ⓢ (23-30W CFL) Add. chain 2996 OZ, add. stem 2999 (12") OZ. Sloped ceiling kit included.
E	43765	OZ	(1) 100W (M)	11.5	12	50	70	36	Ⓢ (18-25W CFL) Add. chain 2996 OZ, add. stem 2999 (12") OZ. Sloped ceiling kit included.

Measurements shown in inches. U.S. & Canada Patent Pending.

CITY LOFT™

NATURAL BRASS, OLDE BRONZE®, OR
POLISHED NICKEL FINISHES WITH SATIN
ETCHED CASED OPAL GLASS



A | 43785 OZ
City Loft™ Pendant



B | 43784 OZ
City Loft™ Pendant



A | 43785 NBR
City Loft™ Pendant



B | 43784 NBR
City Loft™ Pendant



A | 43785 PN
City Loft™ Pendant



B | 43784 PN
City Loft™ Pendant

CITY LOFT™

	ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	L	EXTRA WIRE	CHAIN/STEM	NOTES
A	43785	NBR, OZ, PN	(1) 200W (M)	9	17	55	16.25	38	36	(30-52W CFL) Add. stem 2999 (12") NBR, OZ, PN, add. chain 2996 NBR, OZ, PN.
B	43784	NBR, OZ, PN	(1) 200W (M)	16.25	21.25	60	20.5	30	36	(30-52W CFL) Add. stem 4935 (12") NBR, OZ, PN, add. chain 2996 NBR, OZ, PN.

Measurements shown in inches. U.S. & Canada Patent Pending.



C | 43783 NBR
City Loft™ Pendant



C | 43783 PN
City Loft™ Pendant



Adjustable Arms

C | 43783 OZ
City Loft™ Pendant

CITY LOFT™


ITEM #	FINISH	INCAND. BULB	W	H	OVRL H	L	EXTRA WIRE	CHAIN/STEM	NOTES
C 43783	NBR, OZ, PN	(1) 200W (M)	20.5	25.75	64	25	20	36	(30-52W CFL) Add. stem 4935 (12") NBR, OZ, PN. Add. chain 2996 NBR, OZ, PN. Sloped ceiling kit included.

Measurements shown in inches. U.S. & Canada Patent Pending.



RORY

POLISHED CHROME FINISH WITH
CASED OPAL GLASS SHADE



A | 42951 CH



B | 42952 CH


RORY

	ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/ STEM	NOTES
A	42951	CH	(1) 100W (M)	12	12	50	66	36	Additional stem 2999 (12") CH. Cased Opal Glass Shade with Chrome Edge.
B	42952	CH	(3) 100W (M)	18	15.75	54	68	36	Additional stem 4935 (12") CH. Cased Opal Glass Shade with Chrome Edge.

Measurements shown in inches. U.S. & Canada Patent Pending.

AIDAN

BLACK FINISH WITH INNER GOLD TONE



A | 42796 BK
Pendant



B | 42797 BK
Pendant

AIDAN

	ITEM #	FINISH	INCAND. BULB	W	H	OVRLL. H	EXTRA WIRE	CHAIN/STEM	NOTES
A	42796	BK	(7) 100W (M)	17.25	29	67	72	36	(23-30W CFL) Additional stem 2999 (12") BK, additional chain 2996 BK. Sloped ceiling kit included.
B	42797	BK	(3) 100W (M)	14	29	67	72	36	(23-30W CFL) Additional stem 2999 (12") BK, additional chain 2996 BK. Sloped ceiling kit included.

Measurements shown in inches. U.S. & Canada Patent Pending.

LARKIN™

BRUSHED NICKEL, OLDE BRONZE® OR
STERLING GOLD FINISH



VINTAGE FILAMENT BULB

SOLD SEPARATELY
40W Candelabra Base
5971 CLR



A | 42565 NI
Pendant



A | 42565 OZ
Pendant



A | 42565 SGD
Pendant



B | 42591 NI
Foyer Chandelier



B | 42591 OZ
Foyer Chandelier



B | 42591 SGD
Foyer Chandelier

LARKIN™

	ITEM #	FINISH	INCAND. BULB	W	H	OVRLL. H	EXTRA WIRE	CHAIN/ STEM	NOTES
A	42565	Ni, OZ, SGD	(2) 60W (C)	8	14.75	89	26	72	Additional chain 2996 Ni, OZ, SGD.
B	42591	Ni, OZ, SGD	(8) 60W (C)	24	47.75	122	34	72	Additional chain 2996 Ni, OZ, SGD.

Measurements shown in inches. U.S. & Canada Patent Pending.



C | 42566 NI
Pendant



C | 42566 OZ
Pendant



C | 42566 SGD
Pendant



D | 42568 NI
Foyer Chandelier



D | 42568 OZ
Foyer Chandelier



D | 42568 SGD
Foyer Chandelier

LARKIN™

	ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/STEM	NOTES
C	42566	NI, OZ, SGD	(3) 60W (C)	12	22.25	97	20	72	Additional chain 2996 NI, OZ, SGD.
D	42568	NI, OZ, SGD	(6) 60W (C)	18	36.25	111	7	72	Additional chain 2996 NI, OZ, SGD.

Measurements shown in inches. U.S. & Canada Patent Pending.



SLOANE

BRUSHED NICKEL WITH CLEAR HAMMERED GLASS



A | 43538 NI
Sloane



B | 43537 NI
Sloane

SLOANE

	ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/STEM	NOTES
A	43538	NI	(3) 100W (M)	16	18.5	57	106	36	Hammered Glass Shade.
B	43537	NI	(1) 150W (M)	10.5	17	108	---	---	 (30-52W CFL) Hammered Glass Shade.

Measurements shown in inches. U.S. & Canada Patent Pending.

CARTONE™

OLDE BRONZE® FINISH WITH
NATURAL BRASS ACCENTS



A | 42525 OZ
Pendant



B | 42526 OZ
Pendant

CARTONE™

	ITEM #	FINISH	INCAND. BULB	W	H	OVRLL. H	EXTRA WIRE	CHAIN/STEM	NOTES
A	42525	OZ	(1) 100W (M)	17	20.75	59	69	36	Additional stem 2999 (12") OZ, additional chain 2996 OZ. Sloped ceiling kit included.
B	42526	OZ	(8) 40W (C)	25.5	31.25	70	60	36	Additional stem 2999 (12") OZ, additional chain 2996 OZ. Sloped ceiling kit included.

Measurements shown in inches. U.S. & Canada Patent Pending.

PENDANTS

SHADOW NICKEL & SHADOW BRASS FINISH
WITH CLEAR SEEDED GLASS



A | 43564 SNI
Keller™ Pendant



A | 43564 SBR
Keller™ Pendant



B | 43563 SNI
Keller™ Pendant



B | 43563 SBR
Keller™ Pendant

PENDANTS

	ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/STEM	NOTES
A	43564	SBR, SNI	(1) 100W (M)	15	15.25	53	70	36	☑ (23-30 CFL) Additional stem 4935 SBR, SNI.
B	43563	SBR, SNI	(1) 100W (M)	12	12.75	51	70	36	☑ (23-30 CFL) Additional stem 4935 SBR, SNI.

Measurements shown in inches. U.S. & Canada Patent Pending.

PENDANTS

ANTIQUE PEWTER, BRUSHED NICKEL OR OLDE BRONZE® FINISH



A | 42436 AP Sayre™ Pendant



B | 42437 AP Sayre™ Pendant



Shown as Semi Flush - 15.75" H.



Shown as Semi Flush - 15.75" H.



A | 42436 OZ Sayre™ Pendant



B | 42437 OZ Sayre™ Pendant

CONVERTIBLE

Create two distinct lighting options with one fixture: Semi Flush or Pendant.

C | 42270 NI Keller™



Shown as Pendant - 15.75" H.

CONVERTIBLE

Create two distinct lighting options with one fixture: Semi Flush or Pendant.

C | 42270 OZ Keller™



Shown as Pendant - 15.75" H.

PENDANTS

ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/STEM	NOTES	
A	42436	AP, OZ	(1) 60W (M)	10	8.5	47	70	36	ⓓ Additional chain 2996 AP, OZ additional stem 2999 (12") AP, OZ. Sloped ceiling kit included. Clear Fresnel Lens.
B	42437	AP, OZ	(1) 75W (M)	12	9.25	48	70	36	ⓓ Additional chain 2996 AP, OZ additional stem 2999 (12") AP, OZ. Sloped ceiling kit included. Clear Fresnel Lens.
C	42270	NI, OZ	(1) 100W (M)	12	8.75	47	62	36	ⓓ (23-30W CFL) Add. chain 2996 NI, OZ add. stem 4935 (12") NI, OZ. Sloped ceiling kit incl. Cased Opal Glass.

Measurements shown in inches. U.S. & Canada Patent Pending.



PENDANTS

ASSORTED FINISHES



A | 42610 SGD
Calla Foyer Pendant



B | 42611 SGD
Calla Foyer Pendant



C | 43612 CLP
Halleron™ Pendant



D | 43613 CLP
Halleron™ Chandelier



C | 43612 OZ
Halleron™ Pendant



D | 43613 OZ
Halleron™ Chandelier

PENDANTS

	ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/STEM	NOTES
A	42610	SGD	(2) 60W (C)	10	19.75	94	24	72	Additional chain 2996 SGD.
B	42611	SGD	(3) 60W (C)	14	31	105	14	72	Additional chain 2996 SGD.
C	43612	CLP, OZ	(3) 60W (C)	12	18.5	93	33	72	Additional chain 2996 CLP, OZ.
D	43613	CLP, OZ	(5) 60W (C)	20	30.5	105	17	72	Additional chain 2996 CLP, OZ.

Measurements shown in inches. U.S. & Canada Patent Pending.



E | 43107 CLP
Steeplechase™ Foyer Pendant



F | 43106 CLP
Steeplechase™ Pendant



G | 43105 CLP
Steeplechase™ Pendant



H | 42033 OZ
Foyer Pendant



E | 43107 OZ
Steeplechase™ Foyer Pendant



F | 43106 OZ
Steeplechase™ Pendant



G | 43105 OZ
Steeplechase™ Pendant

PENDANTS

ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/STEM	NOTES	
E	43107	CLP, OZ	(4) 60W (C)	17	29	67	48	36	Additional chain 2996 CLP, OZ, additional stem 2999 (12") CLP, OZ. Sloped ceiling kit included.
F	43106	CLP, OZ	(3) 60W (C)	13	22.5	61	55	36	Additional chain 2996 CLP, OZ, additional stem 2999 (12") CLP, OZ. Sloped ceiling kit included.
G	43105	CLP, OZ	(2) 60W (C)	10	18	56	59	36	Additional chain 2996 CLP, OZ, additional stem 2999 (12") CLP, OZ. Sloped ceiling kit included.
H	42033	OZ	(1) 100W (M)	11	21.75	96	26	72	Ⓜ (23-30W CFL) Additional chain 2996 OZ.

Measurements shown in inches. U.S. & Canada Patent Pending: E, F, G.



PENDANTS

ASSORTED FINISHES



A | 42844 DAW
Pendant



B | 43600 WZC
Pendant



C | 42308 OZ



D | 43717 RS
Rocklyn

PENDANTS

ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/STEM	NOTES
A	DAW	(1) 100W (M)	12	16	90	32	72	☑ (23-30W CFL) Additional chain 2996 DAW.
B	WZC	(3) 100W (M)	15.25	11.75	114	---	---	☑ (23-30W CFL)
C	OZ	(1) 100W (M)	5	8.75	49	61	36	☑ (23-30W CFL) Additional chain 2996 OZ, additional stem 2999 (12") OZ. Sloped ceiling kit included.
D	RS	(3) 100W (M)	17.75	36	74	70	36	Additional chain 2996 RS. Sloped ceiling kit included.

Measurements shown in inches. U.S. & Canada Patent Pending.

PENDANTS

ASSORTED FINISHES WITH WOOD DETAILS



D | 43519 DAG
Basford™ Pendant



Shown as
Semi Flush - 12" H.



Shown as
Semi Flush - 9.2" H.



Shown as
Semi Flush - 7.5" H.



E | 43520 DAG
Basford™ Pendant

CALLEIS™ CONVERTIBLE

Create two distinct lighting options with one fixture:
Semi Flush or Pendant.

C | 43352 RT



Shown as
Pendant - 11.25" H.

ELBUR™ CONVERTIBLE

Create two distinct lighting options with one fixture:
Semi Flush or Pendant.

B | 42644 DBK



Shown as
Pendant - 8.5" H.

ELBUR™ CONVERTIBLE

Create two distinct lighting options with one fixture:
Semi Flush or Pendant.

A | 42643 DBK



Shown as
Pendant - 6.75" H.

PENDANTS

	ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/STEM	NOTES
A	42643	DBK	(1) 100W (M)	10.75	6.75	45	67	36	Additional stem 2999 (12") DBK, additional chain 2996 DBK. Sloped ceiling kit included.
B	42644	DBK	(3) 100W (M)	18	8.5	47	72	36	Additional stem 2999 (12") DBK, additional chain 4901 DBK. Sloped ceiling kit included.
C	43352	RT	(3) 100W (M)	16	11.25	50	74	36	☑️(23-30W CFL) Additional chain 2996 RT, additional stem 2999 (12") RT. Sloped ceiling kit included.
D	43519	DAG	(4) 60W (C)	13	13.5	52	64	36	Additional chain 2996 WZC, additional stem 2999 (12") WZC. Sloped ceiling kit included.
E	43520	DAG	(6) 60W (C)	21	21.25	60	57	36	Additional stem 2999 (12") DBK, additional chain 2996 DBK. Sloped ceiling kit included.

Measurements shown in inches. U.S. & Canada Patent Pending.



DRUM SHADES

BRUSHED NICKEL FINISH
WITH WHITE FABRIC SHADE



Shown as
Semi Flush - 6.5" H.



Shown as
Semi Flush - 7" H.



C | 42196 NI
Pendant

CONVERTIBLE

Create two distinct lighting
options with one fixture:
Semi Flush or Pendant.

A | 42121 NI



Shown as
Pendant - 11.75" H.

CONVERTIBLE

Create two distinct lighting
options with one fixture:
Semi Flush or Pendant.

B | 42122 NI



Shown as
Pendant - 12.25" H.



D | 42197 NI
Oval Pendant

DRUM SHADES

ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	L	STEM TILT	EXTRA WIRE	CHAIN/STEM	NOTES
A	42121	NI (3) 100W (M)	20	11.75	44	---	90°	65	36	Ⓢ (23-30W CFL) Add. stem 2999 (12") NI and/or 2997 (24") NI. Height includes one 6" stem.
B	42122	NI (3) 150W (M)	24	12.25	44	---	90°	64	36	Ⓢ (32-50W CFL) Add. stem 2999 (12") NI and/or 2997 (24") NI. Height includes one 6" stem.
C	42196	NI (5) 100W (M)	30	12	50	---	---	102	36	Ⓢ (32-50W CFL) Add. stem 4935 (12") NI and/or 2997 (24") NI.
D	42197	NI (6) 100W (M)	16	10	48	32	---	106	36	Ⓢ (32-50W CFL) Add. stem 4935 (12") NI and/or 2997 (24") NI.

Measurements shown in inches. U.S. & Canada Patent Pending.

DRUM SHADES

OLDE BRONZE® FINISH
WITH WHITE FABRIC SHADE



A | 42196 OZ
Pendant



Shown as
Semi Flush - 7" H.



Shown as
Semi Flush - 6.5" H.



B | 42197 OZ
Oval Pendant

CONVERTIBLE

Create two distinct lighting options with one fixture:
Semi Flush or Pendant.

C | 42122 OZ



Shown as
Pendant - 12.25" H.

CONVERTIBLE

Create two distinct lighting options with one fixture:
Semi Flush or Pendant.

D | 42121 OZ



Shown as
Pendant - 11.75" H.

DRUM SHADES

	ITEM #	FINISH	INCAND. BULB	W	H	OVRL H	L	STEM TILT	EXTRA WIRE	CHAIN/STEM	NOTES
A	42196	OZ	(5) 100W (M)	30	12	50	---	---	102	36	(23-30W CFL) Additional stem 4935 OZ.
B	42197	OZ	(6) 100W (M)	16	10	48	32	---	106	36	(23-30W CFL) Additional stem 4935 OZ.
C	42122	OZ	(3) 150W (M)	24	12.25	44	---	90°	64	36	(32-50W CFL) Additional stem 2999 (12") OZ. Height includes one 6" stem.
D	42121	OZ	(3) 100W (M)	20	11.75	44	---	90°	65	36	(23-30W CFL) Additional stem 2999 (12") OZ. Height includes one 6" stem.

Measurements shown in inches. U.S. & Canada Patent Pending.

PENDANTS

ASSORTED FINISHES & GLASS



A | 43588 RT
Tippi™ Pendant



B | 78200 AP
Missoula™ Pendant



B | 78200
Missoula™ Pendant




C | 42800 AP
Missoula™ Pendant



C | 42800 BZ
Missoula™ Pendant

PENDANTS

	ITEM #	FINISH	INCAND. BULB	W	H	OVRLL. H	EXTRA WIRE	CHAIN/STEM	NOTES
A	43588	RT	(4) 60W (C)	13	20	58	61	36	Additional chain 2996 RT, additional stem 4935 (12") RT. Sloped ceiling kit included.
B	78200	AP, BZ	(1) 100W (M)	13.5	12.75	87	38	72	 (23-30W CFL) Additional chain 2996 AP, BZ.
C	42800	AP, BZ	(1) 100W (M)	18.5	17.25	92	34	72	Additional chain 2996 AP, BZ. G Type lamp recommended.

Measurements shown in inches. U.S. & Canada Patent Pending.



D | 2714 NI
Grenoble™



E | 2640 NI
Galaxie™



F | 2641 NI
Galaxie™



G | 2643 NI
Galaxie™



H | 42951 CH
Rory



J | 42952 CH
Rory

PENDANTS

	ITEM #	FINISH	INCAND. BULB	W	H	OVRLL. H	STEM TILT	EXTRA WIRE	CHAIN/STEM	HCWO	NOTES
D	2714	NI	(1) 150W (M)	11	8	46	45°	62	36	---	☑ (13-15W CFL) Add. stem 2999 (12") NI and/or 2997 (24") NI.
E	2640	NI	(1) 150W (M)	22.25	9.5	48	45°	68	36	---	Additional stem 2999 (12") and/or 2997 (24") NI.
F	2641	NI	(1) 50W (G9) ⚡	10.25	5	43	45°	62	36	---	Additional stem 2999 (12") NI and/or 2997 (24") NI.
G	2643	NI	(1) 60W (M)	14	5.75	44	45°	76	---	---	Additional stem 2999 (12") and/or 2997 (24") NI.
H	42951	CH	(1) 100W (M)	12	12	50	---	66	36	---	Additional stem 2999 (12") CH.
J	42952	CH	(3) 100W (M)	18	15.75	54	---	68	36	---	Additional stem 4935 (12") CH. Cased Opal Glass Shade with Chrome Edge.

Measurements shown in inches. U.S. & Canada Patent Pending: H, J.



PENDANT & CEILING

ASSORTED FINISHES & GLASS



Shown as
Semi Flush - 9.5" H.



Shown as
Semi Flush - 9.5" H.



B | 42275 NI
Flush Mount



B | 42275 OZ
Flush Mount

CONVERTIBLE

Create two distinct lighting options with one fixture:
Semi Flush or Pendant.

A | 42245 NI



Shown as
Pendant - 9.25" H.

CONVERTIBLE

Create two distinct lighting options with one fixture:
Semi Flush or Pendant.

A | 42245 OZ



Shown as
Pendant - 9.25" H.



C | 42276 NI
Flush Mount



C | 42276 OZ
Flush Mount



D | 42246 NI
Semi Flush



D | 42246 OZ
Semi Flush

PENDANTS

	ITEM #	FINISH	INCAND. BULB	W	H	OVRLL. H	EXTRA WIRE	NOTES
A	42245	NI, OZ	(3) 100W (M)	17.5	9.25	48	64	(23-40W CFL) Additional chain 2996 NI, OZ, additional stem 2999 (12") NI, OZ, and/or 2997 (24") NI. Sloped ceiling kit included.
B	42275	NI, OZ	(3) 60W (M) ✓	17.5	5.5	---	---	(13-40W CFL)
C	42276	NI, OZ	(4) 60W (M) ✦	20.5	5.5	---	---	(13-40W CFL)
D	42246	NI, OZ	(4) 100W (M)	20.5	10.75	---	---	(23-40W CFL)

Measurements shown in inches. U.S. & Canada Patent Pending.



E | 42881 OZ
Nicholson™



E | 42881 NI
Nicholson™



E | 42881 OZU
Nicholson™



F | 3752 NI



G | 2754 NI



H | 2702 NI
Hastings™



H | 2702 TZ
Hastings™

PENDANTS

ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	STEM TILT	EXTRA WIRE	CHAIN/STEM	NOTES
E	42881 NI, OZ, OZU	(1) 150W (M)	16	9.5	84	---	37	72	☑ (30-52W CFL) Additional chain 2996 NI, OZ. G Type lamp recommended. Satin and Umber Etched Glass.
F	3752 NI	(3) 100W (M)	17.5	14	---	---	---	---	☑ (18-25W CFL) Satin Etched White Glass.
G	2754 NI	(4) 150W (M)	26	24	62	45°	87	36	☑ (23-30W CFL) Additional stem 2999 (12") NI, and/or 2997 (24") NI; Satin Etched White Glass.
H	2702 NI, TZ	(1) 150W (M)	17.5	8.5	83	---	36	72	☑ (9-13W CFL) Additional chain 2996 NI, TZ. G Type lamp recommended. Etched Seeded Glass.

Measurements shown in inches.



PENDANTS

ASSORTED FINISHES & GLASS



C | 43201 OZ
Pendant



D | 43200 OZ
Pendant



A | 42466 WMZ
Krasi™ Pendant



B | 42467 WMZ
Krasi™ Mini Pendant



E | 42434 NI
Caparros™



F | 43792 NI
Rowland Pendant

PENDANTS

ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	STEM TILT	EXTRA WIRE	CHAIN/STEM	EXT.	HCWO	NOTES
A	WMZ	(1) 100W (M)	7.75	16.25	55	---	71	36	---	---	☑ (23-30W CFL) Additional chain 2996 WMZ, additional stem 2999 (12") WMZ. Sloped ceiling kit included. Satin Etched Cased Opal Glass.
B	WMZ	(1) 100W (M)	5.5	11	54	---	67	36	6.5	2.5	☑ (23-30W CFL) Additional stem 2999 (12") WMZ. Satin Etched Cased Opal Glass.
C	OZ	(1) 100W (M)	18	10.5	50	90°	66	36	---	---	☑ (23-30W CFL) Additional stem 2999 (12") OZ. Satin Etched Glass.
D	OZ	(1) 100W (M)	13	8.5	48	90°	61	36	---	---	☑ (23-30W CFL) Additional stem 2999 (12") OZ. Satin Etched Glass.
E	NI	(1) 100W (M)	6	7.75	46	---	68	36	---	---	☑ (23-30W CFL) Additional chain 2996 NI, additional stem 2999 (12") NI and/or 2997 NI (24") NI. Sloped ceiling kit included. Clear Inside Ribbed Glass.
F	NI	(1) 100W (M)	8	11.5	50	90°	64	36	---	---	☑ (23-30W CFL) Additional stem 2999 (12") NI. Striated Mirror Glass.

Measurements shown in inches. U.S. & Canada Patent Pending.

PENDANTS INDOOR/OUTDOOR

ASSORTED FINISHES & GLASS



G | 49341 AZ
Bowen™



H | 49205 BK
Tremillo™



J | 49447 AZ, BA
Lyndon™



K | 49446 AZ, BA
Lyndon™



L | 49348 AZ
Pacific Edge™



M | 49640 OZ
Caterham™

PENDANT

ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	L	EXTRA WIRE	CHAIN/STEM	NOTES
G	AZ	(2) 100W (M)	7.25	20.25	95	---	27	72	ⓓ ⓔⓓ (23-30W CFL) Additional chain 4927 AZ. Satin Etched Cased Opal Glass.
H	BK	(1) 100W (M)	6.5	17	91	7	25	72	ⓓ ⓔⓓ (23-30W CFL) Additional chain 4927 BK. Satin Etched Cased Opal Glass.
J	AZ, BA	(1) 100W (M)	6	11.75	50	---	71	36	ⓓ ⓔⓓ (23-30W CFL) Additional chain 4927 AZ, PL, additional stem 2999 (12") AZ, BA. Sloped ceiling kit included. Clear Seeded Glass.
K	AZ, BA	(1) 75W (M)	5	9.5	48	---	72	36	ⓓ ⓔⓓ (18-25W CFL) Additional chain 4927 AZ, PL, additional stem 2999 (12") AZ, BA. Sloped ceiling kit included. Clear Seeded Glass.
L	AZ	(1) 100W (M)	8	13.5	52	---	64	36	ⓓ ⓔⓓ (23-30W CFL) Additional chain 4927 AZ, additional stem 2999 (12") AZ. Sloped ceiling kit included. Satin Etched Cased Opal Glass.
M	OZ	(1) 100W (M)	6.5	16	48	---	58	36	ⓓ ⓔⓓ (23-30W CFL) Additional chain 4927 OZ, additional stem 2999 (12") OZ, Indoor/Outdoor. Sloped ceiling kit included. Satin Etched Cased Opal Glass.

Measurements shown in inches. U.S. & Canada Patent Pending.



PENDANTS INDOOR/OUTDOOR

ASSORTED FINISHES & GLASS



A | 49685 OZ
Pebble Lane



B | 49505 WZC, OZ
Wiscombe Park™



C | 9870 RST
Rustic™



D | 49572 WZC
Ashland Bay



E | 49387 OZ
Manningham™



F | 49582 OZ
Pallerton Way™

PENDANTS INDOOR/OUTDOOR

ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/STEM	NOTES
A	49685 OZ	(1) 150 (M)	9.5	17.75	90	33	72	Ⓧ Additional chain 4927 OZ. Satin Etched Cased Opal Glass.
B	49505 WZC, OZ	(4) 60W (C)	11	23	97	10	72	Ⓧ Additional chain 4927 OZ, WZC. Clear Seeded Glass.
C	9870 RST	(1) 150W (M)	11	17.75	92	29	72	Ⓧ Ⓧ 30D (23-30W CFL) Additional chain 4927 RST. Clear Beveled Glass.
D	49572 WZC	(1) 150W (M)	8.75	17.75	92	28	72	Ⓧ Ⓧ 30D (30-52W CFL) Additional chain 4927 WZC. Clear Seeded Glass.
E	49387 OZ	(3) 60W (C)	8.5	19	93	14	72	Ⓧ Additional chain 4927 OZ. Clear Seeded Glass.
F	49582 OZ	(1) 100W (M)	7.25	17.5	92	30	72	Ⓧ Ⓧ 30D (23-30W CFL) Additional chain 4927 OZ. Etched Seeded Glass.

Measurements shown in inches. U.S. & Canada Patent Pending: A, B, D, E, F.



G | 9809 BK, OZ
9809 OZLED
Mount Vernon



H | 49590 OZ
Larkin™



L | 49294 OZ
Hayman Bay™



M | 49134 BKG, BRZ
Venetian Rain



J | 49556 BKT
Tolerand™



K | 2713 OB, NI
Seaside™

PENDANTS INDOOR/OUTDOOR

ITEM #	LED TEM #	FINISH	INCAND. BULB	LIGHT SOURCE	W	H	OVRL. H	EXTRA WIRE	CHAIN/STEM	NOTES
G 9809	---	OZ, BK	(1) 150W (M)	---	9.5	18.5	57	64	36	Ⓛ Ⓜ Ⓝ (23-30W CFL) Additional chain 4927 BK. Clear Seeded Glass.
---	9809 OZLED	OZ	---	10W Ⓜ	9.5	18.5	93	34	72	Ⓛ Additional chain 4927 BK. Clear Seeded Glass.
H 49590	---	OZ	(4) 100W (M)	---	18	36.75	111	6	72	Ⓛ Ⓜ (23-30W CFL) Additional chain 4927 OZ. Satin Etched Cased Opal Glass.
J 49556	---	BKT	(1) 150W (M)	---	9.5	19.75	94	28	72	Ⓛ Ⓜ Ⓝ (30-52W CFL) Additional chain 4927 BKT. Clear Seeded Glass
K 2713	---	OB, NI	(1) 150W (M)	---	16	13.25	88	36	72	Ⓛ Additional chain 2996 NI, OB. G Type lamp recommended.
L 49294	---	OZ	(1) 100W (M)	---	9	19	93	29	72	Ⓛ Ⓜ Ⓝ (23-30W CFL) Additional chain 4927 OZ. Etched Seeded Glass.
M 49134	---	BKG, BRZ	(2) 60W (C)	---	7.25	24.75	98.75	16	72	Ⓛ Additional chain 4927 BKG, BRZ. Vertical Rain Glass.

Measurements shown in inches. U.S. & Canada Patent Pending: H, J, K, L, M.



LED MINI PENDANTS

Kichler® LED lighting
exceeds the standards
for reliability and beauty

Long-life light emitting diodes (LED)
provide approx. 40,000-hour
life span to L70 (70% initial lumens) –
about 15 years of standard operation.

True optics: pure white light and
controlled beam spread with no
fade or drop off of light.

High Color Rendering Index (CRI)

Standard installation



LED Mini Pendants 42517 OZ | Page 361



B | **42359 WZC**
LED Mini Pendant



A | **42517 CH**
LED Mini Pendant



A | **42517 NI**
LED Mini Pendant



A | **42517 OZ**
LED Mini Pendant

Gold Inside



B | **42359 OZ**
LED Mini Pendant

LED OUTPUT

42517 CH/NI/OZ	650 LUMENS, 14 WATTS 3000 KELVIN, CRI 80, 40K LIFE
42359 OZ/WZC	650 LUMENS, 14 WATTS 3000 KELVIN, CRI 80, 40K LIFE

Visit kichler.com for updated LED Output Specifications.

LED MINI PENDANTS

	LED ITEM #	FINISH	LIGHT SOURCE	W	H	OVRLL. H	STEM TILT	EXTRA WIRE	CHAIN/STEM	NOTES
A	42517	CH, NI, OZ	14W	3	12.25	53	90°	69	36	Additional stem 2999 (12") CH, NI, OZ and/or 2997 (24") NI.
B	42359	OZ, WZC	14W	6	7	47.5	90°	69	36	Additional stem 2999 (12") OZ, WZC. Dimmable.

Measurements shown in inches. U.S. & Canada Patent Pending.



MINI
PENDANTS



Mini Pendants 43200 OZ and 43201 OZ | Page 363



A | 43489 BKGLD
Annata™
Gold Shade



A | 43489 BKSLV
Annata™
Silver Shade



B | 43486 NIBL
Aquilino™



C | 42432 AP
Mini Pendant



D | 43201 OZ
Pendant



E | 43200 OZ
Pendant




F | 43488 OZ
Kinny™

MINI PENDANTS

ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	STEM TILT	EXTRA WIRE	CHAIN/STEM	NOTES
A	43489 BKGLD, BKSLV	(1) 100W (M)	6.25	8.5	114	---	---	---	☑ (23-30W CFL) Ceramic Shade.
B	43486 NIBL	(1) 100W (M)	6	11.25	50	---	68	36	Additional stem 2999 (12") NI and/or stem 2997 (24") NI.
C	42432 AP	(1) 100W (M)	4.5	12.75	51	---	64	---	☑ (23-30W CFL) Add. chain 2996 AP, add. stem 2999 (12") AP. Sloped ceiling kit incl.
D	43201 OZ	(1) 100W (M)	18	10.5	50	90°	66	36	☑ (23-30W CFL) Additional stem 2999 (12") OZ.
E	43200 OZ	(1) 100W (M)	13	8.5	48	90°	61	36	☑ (23-30W CFL) Additional stem 2999 (12") OZ.
F	43488 OZ	(1) 100W (M)	8.25	14.5	53	---	65	36	Additional stem 2999 (12") OZ.

Measurements shown in inches. U.S. & Canada Patent Pending.



MINI PENDANTS

ASSORTED FINISHES & GLASS



A | 42308 OZ



B | 43602 WZC
Industrial Cage



C | 43127 NBR
Devin



D | 43551 CLP
Devin



D | 43551 NBR
Devin

MINI PENDANTS

	ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/STEM	NOTES
A	42308	OZ	(1) 100W (M)	5	8.75	49	61	36	Additional chain 2996 OZ, additional stem 2999 (12") OZ. Sloped ceiling kit included.
B	43602	WZC	(1) 100W (M)	6.75	11	49	---	---	
C	43127	NBR	(1) 100W (M)	7.75	10.25	48	---	---	
D	43551	CLP, NBR	(1) 100W (M)	8	9	46	---	---	CLP: Prismatic Clear Glass, NBR: Prismatic Smoke Glass.

Measurements shown in inches. U.S. & Canada Patent Pending: B, C.



E | 42878 OZ
Brinley™



E | 42878 NI
Brinley™



H | 43589 NBR
Rumer™



J | 49587 OZ
Westington™ Indoor/Outdoor



F | 43584 AVI
Ahrendale™



G | 43719 RS
Rocklyn

MINI PENDANTS

ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/STEM	EXT.	HCWO	NOTES
E	42878 NI, OZ	(1) 100W (M)	4.75	7.75	45	---	---	---	---	Ⓜ (23-30W CFL)
F	43584 AVI	(1) 100W (M)	6	13	51	61	36	---	---	Ⓜ (23-30W CFL) Additional chain 2996 AVI, additional stem 2999 (12") AVI. Sloped ceiling kit included.
G	43719 RS	(1) 100W (M)	8	9.25	46	---	---	---	---	
H	43589 NBR	(1) 60W (M)	5	13.5	46	50	---	5.25	2.5	Additional chain 2996 NBR, additional stem 2999 (12") NBR. Height does not include bulb. Height includes 6" stem. Sloped ceiling kit included.
J	49587 OZ	(1) 100W (M)	12	3.75	42	67	36	---	---	Ⓜ Additional chain 2999 (12") OZ, additional chain 2996 OZ. Sloped ceiling kit included.

Measurements shown in inches. U.S. & Canada Patent Pending.



PENELOPE

BRUSHED NICKEL AND OLDE BRONZE® FINISH
WITH CLEAR SEEDED GLASS



A | 42324 NI
Mini Pendant



A | 42324 OZ
Mini Pendant

PENELOPE

ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/STEM	NOTES
A 42324	NI, OZ	(1) 100W (M)	7.75	10	49	66	36	(23-30W CFL) Additional chain 2996 NI, OZ, additional stem 2999 (12") NI, OZ and/or 2997 (24") NI. Sloped ceiling kit included. Organized Seeded Glass Shade.


Measurements shown in inches. U.S. & Canada Patent Pending.

HOLBROOK

NATURAL BRASS, BRUSHED NICKEL OR
OLDE BRONZE® WITH CLEAR SEEDED GLASS



A | 42588 NBR
Mini Pendant



A | 42588 NI
Mini Pendant



A | 42588 OZ
Mini Pendant

HOLBROOK


ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/STEM	NOTES
A 42588	NBR, NI, OZ	(2) 60W (M)	10	12	50	59	36	Additional chain 2996 NBR, NI, OZ, additional stem 2999 (12") NBR, NI, OZ, and/or 2997 (24") NI. Sloped ceiling kit included.

Measurements shown in inches. U.S. & Canada Patent Pending.



AVERY

POLISHED CHROME, BRUSHED NICKEL &
OLDE BRONZE® FINISH WITH
CLEAR SEEDED GLASS



A | 43853 CH



B | 43850 CH



A | 43853 NI



A | 43853 OZ



B | 43850 NI



B | 43850 OZ

AVERY

	ITEM #	FINISH	INCAND. BULB	W	H	OVRLL. H	NOTES
A	43853	CH, NI, OZ	(1) 100W (M)	10	9.25	46	(23-30W CFL) Functioning on/off paddle switch.
B	43850	CH, NI, OZ	(1) 100W (M)	8	8.25	45	(23-30W CFL) Functioning on/off paddle switch.

Measurements shown in inches. U.S. & Canada Patent Pending.



C | 43851 CH



C | 43851 NI



C | 43851 OZ



D | 43852 CH



D | 43852 NI



D | 43852 OZ

AVERY

	ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	NOTES
C	43851	CH, NI, OZ	(1) 100W (M)	8.25	8.75	46	☑ (23-30W CFL) Functioning on/off paddle switch.
D	43852	CH, NI, OZ	(1) 100W (M)	9.75	9.5	48	☑ (23-30W CFL) Functioning on/off paddle switch.

Measurements shown in inches. U.S. & Canada Patent Pending.



MINI PENDANTS

ASSORTED FINISHES & GLASS



A | **65407**
Crystal Ball™
Silver Mosaic
Crackle Glass



B | **65408**
Crystal Ball™
Teal Mosaic
Crackle Glass



C | **65406**
Crystal Ball™
Bronze Mosaic
Crackle Glass

MINI PENDANTS

ITEM #	INCAND. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/STEM	NOTES
A 65407	(1) 100W (M)	8	12.75	51	67	---	Ⓜ (23-30W CFL) Additional chain 2996 NI, additional stem 2999 (12") NI and/or 2997 (24") NI. Sloped ceiling kit included.
B 65408	(1) 100W (M)	8	12.75	51	67	36	Ⓜ (23-30W CFL) Additional chain 2996 NI, additional stem 2999 (12") NI and/or 2997 (24") NI. Sloped ceiling kit included.
C 65406	(1) 100W (M)	8	12.75	51	67	36	Ⓜ (23-30W CFL) Additional chain 2996 NI, additional stem 2999 (12") NI and/or 2997 (24") NI. Sloped ceiling kit included.

Measurements shown in inches. U.S. & Canada Patent Pending.



D | 42123 CH
Reynes™



E | 3030 NI
Modena™



F | 43682 WH
Danika

MINI PENDANTS

	ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	STEM TILT	EXTRA WIRE	CHAIN/STEM	NOTES
D	42123	CH	(1) 100W (M)	4	14	46	45°	67	36	☑ (18-25W CFL) Additional stem 2999 (12") CH. Height includes one 6" stem.
E	3030	NI	(1) 100W (M)	3.5	6.5	45	45°	68	36	☑ (18-25W CFL) Additional chain 2996 NI, additional stem 2999 (12") NI and/or 2997 (24") NI. Sloped ceiling kit included.
F	43682	WH	(1) 100W (M)	5.25	9.25	---	---	---	---	☑ (23-30W CFL) G Type lamp recommended.

Measurements shown in inches. U.S. & Canada Patent Pending: A, C.



MINI PENDANTS

ASSORTED FINISHES & GLASS



A | 43371 OZ
Tremba™



B | 43755 AUB
Cirus™



C | 42384 AP
Lacey™



C | 42384 MIZ
Lacey™



D | 42467 WMZ
Krasi™



E | 42466 WMZ
Krasi™

MINI PENDANTS

ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	STEM TILT	EXTRA WIRE	CHAIN/STEM	EXT.	HCWO	NOTES
A	43371 OZ	(1) 100W (M)	6.25	12.25	50	---	60	36	---	---	Ⓜ (23-30W CFL) Additional chain 2996 OZ, additional stem 2999 (12") OZ. Sloped ceiling kit included.
B	43755 AUB	(1) 100W (M)	8	8.5	47	---	66	36	---	---	Ⓜ (18-25W CLF) Additional stem 2999 (12") NI and/or 2997 (24") NI.
C	42384 AP, MIZ	(1) 60W (C) Ⓜ	6	10.25	49	90°	54	---	---	---	Additional chain 2996 AP, MIZ. Krypton bulb included.
D	42467 WMZ	(1) 100W (M)	5.5	11	54	---	67	36	6.5	2.5	Ⓜ (23-30W CFL) Additional stem 2999 (12") WMZ.
E	42466 WMZ	(1) 100W (M)	7.75	16.25	55	---	71	36	---	---	Ⓜ (23-30W CFL) Additional chain 2996 WMZ, additional stem 2999 (12") WMZ.

Measurements shown in inches. U.S. & Canada Patent Pending.



F | 43624 NI
Evie



G | 43625 NI
Evie



H | 43629 NI
Evie



J | 42174 CH
Crystal Skye™



K | 42484 OZ
Leighton™



L | 43568 OZ
Casilda™



L | 43568 SGD
Casilda™

MINI PENDANTS

ITEM #	FINISH	INCAND. BULB	W	H	STEM TILT	OVRL. H	EXTRA WIRE	CHAIN/STEM	NOTES
F	NI	(1) 100W (M)	6.5	7.75	---	45	---	---	
G	NI	(1) 100W (M)	6	9.5	---	47	---	---	
H	NI	(1) 100W (M)	6	8.25	---	45	---	---	
J	CH	(1) 100W (M)	6.5	11.5	---	85	---	---	☑ (23-30W CFL)
K	OZ	(1) 60W (C) ⚡	8	18.5	---	56.5	50	36	Additional chain 2996 OZ, additional stem 2999 (12") OZ. Krypton light source.
L	OZ, SGD	(1) 100W (M)	7	13.5	90°	52	61	36	☑ (23-30W CFL) Additional stem 2999 (12") OZ.

Measurements shown in inches. U.S. & Canada Patent Pending.



LED DIRECTIONAL RAIL LIGHTS

Kichler® LED lighting
exceeds the standards
for reliability and beauty

Long-life light emitting diodes (LED)
provide approx. 40,000-hour
life span to L70 (70% initial lumens) –
about 15 years of standard operation.

True optics: pure white light and
controlled beam spread with no
fade or drop off of light.

High Color Rendering Index (CRI)

Standard installation



LED Directional Rail Light 10326 NI | Page 375

LED DIRECTIONAL RAIL LIGHTS

VERSATILE 3 OR 4-LIGHT, SWIVEL-HEAD WALL OR CEILING MOUNTED FIXTURE FOCUSES LIGHT IN MULTIPLE DIRECTIONS. IDEAL FOR HALLWAYS, BATHS AND SETTINGS THAT DEMAND ATTENTION. LAMPS SWIVEL 90° AND ROTATE 330°.



A | 10326 NI



B | 10325 NI



These devices comply with part 15 of the FCC Regulations.

LED OUTPUT

10325 NI	1075 LUMENS, 23 WATTS 2700 KELVIN, CRI 80, 40K LIFE
10326 NI	1000 LUMENS, 23 WATTS 2700 KELVIN, CRI 80, 40K LIFE

Visit kichler.com for updated LED Output Specifications.

LED DIRECTIONAL RAIL LIGHTS

	LED ITEM #	FINISH	LIGHT SOURCE	W	H	L	EXT.	HCWO	NOTES
A	10326	NI	(4) 6.6W	5.75	11.5	35.25	10.5	3	May be ceiling or wall mounted, 90° vertical rotation, 330° horizontal rotation. Satin Etched Glass. Dimmable
B	10325	NI	(4) 6.6W	6.25	9.5	33.5	8.5	3.25	May be ceiling or wall mounted, 90° vertical rotation, 330° horizontal rotation. Clear Polished Glass with Inside Etch. Dimmable.

Measurements shown in inches. U.S. & Canada Patent Pending.

DIRECTIONAL RAIL LIGHTS

ASSORTED FINISHES & GLASS



A | 7772 CH
Hendrik™



A | 7772 NI
Hendrik™



A | 7772 OZ
Hendrik™



B | 42164 AP
Bellamy™



B | 42164 OZ
Bellamy™

DIRECTIONAL RAIL LIGHTS

	ITEM #	FINISH	INCAND. BULB	W	H	L	EXT.	HCWO	NOTES
A	7772	CH, NI, OZ	(4) 50W (GU10)	5	8.25	30	6.25	2.5	Ⓧ May be ceiling or wall mounted, Halogen light source.
B	42164	AP, OZ	(4) 50W (GU10)	5.5	8.75	34.25	7.5	2.75	Ⓧ May be ceiling or wall mounted, Halogen light source. OZ: Umber Etched Glass.

Measurements shown in inches. U.S. & Canada Patent Pending: A.



C | 42439 OZ
Sayre™



COORDINATING CEILING FAN

See the full line of Kichler®
Ceiling Fans in catalog K416
or visit kichler.com

D | 300114 OZ



E | 7050 OZ
Hatteras Bay™



E | 7050 PN
Hatteras Bay™



F | 7704 PN
Hatteras Bay™



F | 7704 OZ
Hatteras Bay™

DIRECTIONAL RAIL LIGHTS

	ITEM #	FINISH	INCAND. BULB	W	H	L	EXT.	HCWO	NOTES
C	42439	OZ	(3) 50W (GU10) ✓	6	9.75	24	7.5	3	ⓓ May be ceiling or wall mounted, Halogen light source.
D	300114	OZ	---	---	---	---	---	---	See the full line of Kichler® Ceiling Fans in catalog K416 or visit kichler.com .
E	7050	OZ, PN	(3) 50W (GU10) ✓	5.5	11.25	22.75	7.25	2.75	ⓓ May be ceiling or wall mounted, Halogen light source.
F	7704	OZ, PN	(4) 50W (GU10) ✓	5.5	11.25	31.25	7.5	2.75	ⓓ May be ceiling or wall mounted, Halogen light source.

Measurements shown in inches. U.S. & Canada Patent Pending.




CEILING

FORM & FUNCTION

Long live the ceiling fixture, with its room-filling (and essential!) ambient light. With Kichler's diverse offering, you'll find high style is also part of the equation. Simple and understated or flashy and glamorous – our collections put light right where you need in a way that enhances a room's overall decor. Plus, our energy efficient options assure that this often-used fixture delivers light sensibly. Flip a switch, and let the transformation begin.





Hatteras Bay™ 43883 OZLED | Page 380 & Brinley™ 42891 OZ | Page 383

LED CEILING

Long-life light emitting diodes (LED) provide approx. 40,000-hour life span to L70 (70% initial lumens) – about 15 years of standard operation.

True optics: pure white light and controlled beam spread with no fade or drop off of light.

High Color Rendering Index (CRI)

Standard installation



These devices comply with part 15 of the FCC Regulations.

LED OUTPUT

8112 NILED/OZLED	1750 LUMENS, 25 WATTS, 3000 KELVIN, CRI 80, 40K LIFE
8116 NILED/OZLED	1750 LUMENS, 25 WATTS, 3000 KELVIN, CRI 80, 40K LIFE
42379 NI/OZ	1600 LUMENS, 25 WATTS, 3000 KELVIN, CRI 80, 40K LIFE
42380 NI/OZ	1600 LUMENS, 25 WATTS, 3000 KELVIN, CRI 80, 40K LIFE
43649 CHLED	1200 LUMENS, 25 WATTS, 3000 KELVIN, CRI 80, 40K LIFE
43650 CHLED	1450 LUMENS, 25 WATTS, 3000 KELVIN, CRI 80, 40K LIFE
43845 WHLED	535 LUMENS, 12 WATTS, 3000/2700 KELVIN, CRI 90, 40K LIFE
43846 WHLED	850 LUMENS, 15 WATTS, 3000/2700 KELVIN, CRI 90, 40K LIFE



A | 43875 NILED



A | 43875 OZLED



B | 43876 NILED



B | 43876 OZLED



C | 43877 NILED



C | 43877 OZLED



D | 43883 NILED
Hatteras Bay™



D | 43883 OZLED
Hatteras Bay™



D | 43883 PNLED
Hatteras Bay™



E | 43885 NILED
Hatteras Bay™



E | 43885 OZLED
Hatteras Bay™



E | 43885 PNLED
Hatteras Bay™



F | 42380 NI



F | 42380 OZ



G | 43649 CHLED Savoca™



H | 42379 NI



H | 42379 OZ



J | 43650 CHLED Savoca™



K | 8112 NILED



K | 8112 OZLED



L | 43845 WHLED27



L | 43845 WHLED30



M | 8116 NILED



M | 8116 OZLED



N | 43846 WHLED27



N | 43846 WHLED30

LED CEILING

	LED ITEM #	FINISH	LIGHT SOURCE	W	H	L	NOTES
A	43875 NILED / 43875 OZLED	NI, OZ	22W	16	3.75	16	Satin Etched Glass.
B	43876 NILED / 43876 OZLED	NI, OZ	24W	18	3.5	18	Satin Etched Glass.
C	43877 NILED / 43877 OZLED	NI, OZ	29W	24	3.5	24	Satin Etched Glass.
D	43883 NILED / 43883 OZLED / 43883 PNLED	NI, OZ, PN	22W	13.25	4.5	---	Inside Etched Clear Fresnel Lens.
E	43885 NILED / 43885 OZLED / 43885 PNLED	NI, OZ, PN	22W	18	5	---	Inside Etched Clear Fresnel Lens.
F	42380	NI, OZ	25W	14	3.25	---	Inside Etched Clear Fresnel Lens.
G	43649 CHLED	CH	24W	15	6.75	15	Etched White Glass. Dimmable.
H	42379	NI, OZ	25W	13.25	3.25	---	Opal Etched Glass.
J	43650 CHLED	CH	24W	18	2.5	18	Etched White Glass. Dimmable.
K	8112 NILED / 8112 OZLED	NI, OZ	25W	13.25	6	---	Satin Etched Glass. Dimmable.
L	43845 WHLED27 / 43845 WHLED30	WH	12W	6	1.25	---	Frosted Lens. Dimmable. Retrofit ceiling adaptor 4145LED.
M	8116 NILED / 8116 OZLED	NI, OZ	25W	15.25	6.5	---	Satin Etched Glass. Dimmable.
N	43846 WHLED27 / 43846 WHLED30	WH	15W	7.5	1.25	---	Frosted Lens. Dimmable. Retrofit ceiling adaptor 4146LED.

Measurements shown in inches. U.S. & Canada Patent Pending: F, G, H, J.



CEILING

ASSORTED FINISHES & GLASS



A | 43909 CLP
Grayson



A | 43909 NBR
Grayson



B | 43740 CLP
Silberne™



B | 43740 NBR
Silberne™



C | 3620 NI



D | 3627 NI



D | 3627 OZ



E | 3623 NI



E | 3623 TZ



E | 3623 OZ



F | 42025 NI



F | 42025 OZ

CEILING

ITEM #	FINISH	INCAND. BULB	W	H	NOTES
A	CLP, NBR	(2) 75W (M) A19 ✦	17	5	☑ (18-25W CFL) CLP, NBR: Satin Etched Cased Opal Glass.
B	CLP, NBR	(3) 60W (M)	18	10	CLP, NBR: Clear Seeded Glass.
C	NI	(2) 100W (M) ✦	13.5	7.25	☑ (13-15W CFL) NI: White Etched Glass, OZ: Umber Etched Glass.
D	NI, OZ	(3) 100W (M) ✦	15	7.75	☑ (9-13W CFL) NI: White Etched Glass, OZ: Umber Etched Glass.
E	NI, OZ, TZ	(3) 60W (M)	15.25	14	☑ (13-15W CFL) NI, TZ: Etched Seeded Glass; OZ: Umber Etched Seeded Glass.
F	NI, OZ	(4) 100W (M)	23.25	10	☑ (23-30W CFL) NI: Satin Etched White Glass.

Measurements shown in inches.



G | 3718 NI



G | 3718 TZ



H | 3122 NIA



H | 3122 NI



H | 3122 TZ



J | 42891 NI
Flush Mount



J | 42891 OZ
Flush Mount



K | 42245 NI
Semi Flush



K | 42245 OZ
Semi Flush



L | 42246 NI
Semi Flush



L | 42246 OZ
Semi Flush

CEILING

ITEM #	FINISH	INCAND. BULB	W	H	OVRLL. H	EXTRA WIRE	NOTES	
E	3718	NI, TZ	(2) 100W (M)	13	10.5	---	---	☑ (13-15W CFL) NI, TZ: Satin Etched Glass.
F	3122	NI, NIA, TZ	(3) 100W (M)	15	9.75	---	---	☑ (18-25W CFL) NI, TZ: Satin Etched Glass, NIA: Alabaster Swirl Glass.
G	42891	NI, OZ	(3) 75W (M) ✓	11	8	---	---	(18-25W CFL) Clear Glass.
H	42245	NI, OZ	(3) 100W (M)	17.5	9.25	48	64	☑ (23-40W CFL) Additional chain 2996 NI, OZ, additional stem 2999 (12") NI, OZ and/or 2997 (24") NI. Sloped ceiling kit included. Satin Etched White Glass.
J	42246	NI, OZ	(4) 100W (M)	20.5	10.75	---	---	☑ (23-40W CFL) Satin Etched White Glass.

Measurements shown in inches. U.S. & Canada Patent Pending: G, H, J.



CEILING

ASSORTED FINISHES & GLASS



A | 8108 NI



A | 8108 OZ



A | 8108 TZ



B | 8109 NI



B | 8109 OZ



B | 8109 TZ



C | 8110 NI



C | 8110 OZ



C | 8110 TZ



D | 8653 NI



D | 8653 SC



D | 8653 TZ



E | 8654 NI



E | 8654 SC



E | 8654 TZ



F | 8655 NI



F | 8655 SC



F | 8655 TZ

CEILING ENERGY EFFICIENT

ASSORTED FINISHES & GLASS



G | 10835 ESNI



H | 10836 NI



H | 10836 OZ



H | 10836 WH



J | 10837 NI



K | 8880 NIFL



L | 8881 NIFL

CEILING

	ITEM #	FINISH	INCAND. BULB	W	H	NOTES
A	8108	NI, OZ, TZ	(2) 60W (M) ❖	11.25	6.25	Ⓜ (13-15W CFL) NI, TZ: Alabaster Swirl Glass, OZ: Light Umber Etched Glass.
B	8109	NI, OZ, TZ	(2) 60W (M) ❖	13.25	6	Ⓜ (13-15W CFL) NI, TZ: Alabaster Swirl Glass, OZ: Light Umber Etched Glass.
C	8110	NI, OZ, TZ	(3) 60W (M) ✓	15.25	7	Ⓜ (13-15W CFL) NI, TZ: Alabaster Swirl Glass, OZ: Light Umber Etched Glass.
D	8653	NI, SC, TZ	(2) 60W (M) ❖	11.5	6	Ⓜ (13-15W CFL) Satin Etched Glass.
E	8654	NI, SC, TZ	(2) 60W (M) ❖	13.25	5.5	Ⓜ (13-15W CFL) Satin Etched Glass.
F	8655	NI, SC, TZ	(3) 60W (M) ❖	15.25	6.25	Ⓜ (13-15W CFL) Satin Etched Glass.

Measurements shown in inches.

CEILING ENERGY EFFICIENT

	FLUOR. ITEM #	FINISH	FLUOR. BULB	W	H	NOTES
G	10835	ESNI	(1) 18W (GU24) Ⓜ Ⓟ Ⓠ	11.25	6	NI: Alabaster Swirl Glass.
H	10836	NI, OZ, WH	(2) 13W (GU24) Ⓜ Ⓟ Ⓠ	13.25	6	NI, WH: Alabaster Swirl Glass, OZ: Light Umber Etched Glass. OZW: White Glass. (2) 18W bulbs included.
J	10837	NI	(2) 13W (GU24) Ⓜ Ⓟ Ⓠ	15.5	7	NI: Alabaster Swirl Glass.
K	8880 NIFL	NI	(1) 18W (GU24) Ⓜ Ⓠ	10	4.25	Ⓧ Satin Etched Cased Opal Twist-On Glass.
L	8881 NIFL	NI	(2) 13W (GU24) Ⓜ Ⓠ	14	4.75	Ⓧ Satin Etched Cased Opal Twist-On Glass.

Measurements shown in inches.



CEILING

ASSORTED FINISHES & GLASS



A | 8111 AP



A | 8111 CH



A | 8111 NI



A | 8111 OZ



B | 8112 AP



B | 8112 CH



B | 8112 NI



B | 8112 OZ



C | 8116 AP



C | 8116 CH



C | 8116 NI



C | 8116 OZ



D | 216 WH



E | 9834 WH
Indoor/Outdoor Ceiling

CEILING

ITEM #	FINISH	INCAND. BULB	W	H	NOTES
A	8111 : AP, CH, NI, OZ	(2) 60W (M) ❖	11.25	6.25	☑ (13-15W CFL) Satin Etched Glass.
B	8112 : AP, CH, NI, OZ	(2) 60W (M)	13.25	6	☑ (13-15W CFL) Satin Etched Glass.
C	8116 : AP, CH, NI, OZ	(3) 60W (M)	15.25	6.5	☑ (13-15W CFL) Satin Etched Glass.
D	216 : WH	(1) 75W (M) ✓	5.75	7	☑ (18-25W CFL) White Glass.
E	9834 : WH	(1) 65W (M) ❖	4.5	8.5	☑ (23-30W CFL)

Measurements shown in inches.



F | 8404 NI



G | 8405 NI



G | 8405 TZ



H | 8406 NI



J | 8407 TZ



J | 8407 NI



K | 42275 NI
Flush Mount



L | 42276 NI
Flush Mount



K | 42275 OZ
Flush Mount



L | 42276 OZ
Flush Mount

CEILING

	ITEM #	FINISH	INCAND. BULB	W	H	NOTES
F	8404	NI	(1) 100W (M)	12	6.25	NI: Etched White Glass, TZ: Etched Sunset Glass.
G	8405	NI, TZ	(2) 75W (M) ❖	15	6	NI: Etched White Glass, TZ: Etched Sunset Glass.
H	8406	NI	(3) 60W (M) ✓	17	6.5	NI: Etched White Glass, TZ: Etched Sunset Glass.
J	8407	NI, TZ	(5) 75W (M) ❖	25	9.5	NI: Etched White Glass, TZ: Etched Sunset Glass.
K	42275	NI, OZ	(3) 60W (M) ✓	17.5	5.5	Ⓜ (13-40W CFL) Satin Etched White Glass.
L	42276	NI, OZ	(4) 60W (M) ❖	20.5	5.5	Ⓜ (13-40W CFL) Satin Etched White Glass.

Measurements shown in inches. U.S. & Canada Patent Pending: K, L.



CEILING

ASSORTED FINISHES & GLASS



A | 42266 NI



A | 42266 OZ



A | 42266 CH



B | 206 NI



B | 206 OZ



B | 206 WH



C | 8206 NI



D | 208 WH



E | 209 NI



E | 209 OZ



E | 209 WH



F | 8209 NI



G | 210 WH



H | 7350 WH

CEILING

ITEM #	FINISH	INCAND. BULB	W	H	NOTES
A	42266 : CH, NI, OZ	(1) 100W (M) ✓	7	7.5	☑ (23-30W CFL) Cased Opal Glass.
B	206 : NI, OZ, WH	(1) 60W (M) ✓	7.5	5	☑ (9-13W CFL) White Glass.
C	8206 : NI	(1) 60W (M) ✓	7.5	5	☑ (13-15W CFL) Alabaster Swirl Glass.
D	208 : WH	(1) 100W (M)	9.25	5	☑ (18-25W CFL) White Glass.
E	209 : NI, OZ, WH	(2) 60W (M) ❖	9.25	5	White Glass.
F	8209 : NI	(2) 60W (M) ❖	9.25	5.5	Alabaster Swirl Glass.
G	210 : WH	(2) 75W (M) ❖	12	6.75	White Glass.
H	7350 : WH	(3) 60W (M) ✓	15.25	7.5	☑ (13-15W CFL) White Glass.

Measurements shown in inches. U.S. & Canada Patent Pending: A.



J | 8102 NI
8102 NIFL
8103 NIFL



J | 8102 WH
8102WHFL



K | 8880 NI
8880 NIFL



K | 8880 OZ



K | 8880 WH



L | 8881 NI
8881 NIFL



L | 8881 OZ



L | 8881 WH



M | 8882 NI



N | 7003 NI



O | 8064 NI



O | 8064 TZ



P | 8065 NI



P | 8065 TZ



Q | 9817 AP



R | 7260 WH

CEILING

ITEM #	FLUOR. ITEM #	FINISH	INCAND. BULB	FLUOR. BULB	W	H	NOTES
J	8102	---	(2) 60W (M) ❖	---	9.25	4.75	☑ (13-15W CFL) White Clip-On Glass.
J	---	8102 NIFL / 8102 WHFL	---	(2) 13W (GU24) ✓ Ⓢ Ⓜ Ⓡ	9.25	5.25	White Clip-On Glass.
J	---	8103 NIFL	---	(3) 13W (GU24) Ⓢ Ⓡ	11.75	6.5	White Clip-On Glass.
K	8880	---	(1) 75W (M) ❖	---	10	4.25	Ⓢ Satin Etched Cased Opal Twist-On Glass.
K	---	8880 NIFL	---	(1) 18W (GU24) Ⓢ Ⓡ	10	4.25	Ⓢ Satin Etched Cased Opal Twist-On Glass.
L	8881	---	(1) 100W (M) ❖	---	14	4.75	Ⓢ Satin Etched Cased Opal Twist-On Glass.
L	---	8881 NIFL	---	(2) 13W (GU24) Ⓢ Ⓡ	14	4.75	Ⓢ Satin Etched Cased Opal Twist-On Glass.
M	8882	---	(2) 75W (M) ❖	---	16.5	5.5	Ⓢ (18-25W CFL) Satin Etched Cased Opal Twist-On Glass.
N	7003	---	(2) 60W (M) ❖	---	13	4.5	☑ (9-13W CFL) NI: Satin Etched Glass.
O	8064	---	(2) 60W (M) ❖	---	13.25	6.25	☑ (13-15W CFL) Etched Seeded Glass.
P	8065	---	(3) 60W (M) ❖	---	15.25	7.75	☑ (13-15W CFL) Etched Seeded Glass.
Q	9817	---	(2) 100W (M) ✓	---	13	7	Ⓢ ☑ (18-25W CFL) AP: Satin Etched Glass.
R	7260	---	(2) 60W (M) ✓	---	12	5.5	☑ (13-15W CFL) White Glass.

Measurements shown in inches. U.S. & Canada Patent Pending: P.



CEILING ENERGY EFFICIENT

ASSORTED FINISHES & GLASS



A | 10885 NI
Santiago



B | 10886 NI
Santiago



C | 10803 BA
Pira™



D | 10804 BA
Pira™



E | 10898 NI
Ara



F | 10824 CP

CEILING ENERGY EFFICIENT

	FLUOR. ITEM #	FINISH	FLUOR. BULB	W	H	NOTES
A	10885	NI	(2) 13W (QAD4)	13	4.25	White Linen Fabric Trim Ring with Matte White Acrylic Diffuser.
B	10886	NI	(3) 13W (QAD4)	17.25	4.25	White Linen Fabric Trim Ring with Matte White Acrylic Diffuser.
C	10803	BA	(1) 40W (CLFL)	12	4	White Vinyl Laminate Trim Ring with Matte White Acrylic Diffuser.
D	10804	BA	(1) 55W (CLFL)	15	4	White Vinyl Laminate Trim Ring with Matte White Acrylic Diffuser.
E	10898	NI	(1) 70W (CLFL)	20	8	Matte White Acrylic Diffuser.
F	10824	CP	(3) 18W (GU24)	22	6	Acrylic Applied Tint with Painted Linen.

Measurements shown in inches.



G | 10890 WH



H | 10891 WH



J | 10827 NI



J | 10827 OZ



K | 10828 NI



K | 10828 OZ



L | 10879 NI



L | 10879 OZ

Oval Shape

CEILING ENERGY EFFICIENT

	FLUOR. ITEM #	FINISH	FLUOR. BULB	W	H	L	EXTRA WIRE	NOTES
G	10890	WH	(1) 22W / 32W (T9)	13.75	2.75	---	---	Matte White Acrylic Diffuser.
H	10891	WH	(1) 32W / 40W (T9)	18.25	3.75	---	---	Matte White Acrylic Diffuser.
J	10827	NI, OZ	(2) 26W (PLFL)	16	3.25	---	---	White Acrylic Diffuser.
K	10828	NI, OZ	(3) 26W (PLFL)	24	4.75	---	6.5	White Acrylic Diffuser.
L	10879	NI, OZ	(2) 36W (QAD4)	18.25	4.5	32.5	---	White Acrylic Diffuser.

Measurements shown in inches.



CEILING ENERGY EFFICIENT

ASSORTED FINISHES & GLASS



A | 10802 SI
Pavillion™



D | 10847 OZ
Chella™



B | 10425 BA
Pira™



Flush or Semi Flush mounted.
Flush mount 4.25" H.











C | 10314 WH



D | 10847 SI
Chella™

CEILING ENERGY EFFICIENT

	FLUOR. ITEM #	FINISH	FLUOR. BULB	W	H	L	
A	10802	SI	(4) 32W (BIPI)  	16.25	5	52.25	 Matte White Acrylic Diffuser.
B	10425	BA	(2) 32W (BIPI) 	10.25	3.75	50	 Brushed Aluminum with Matte White Acrylic Diffuser.
C	10314	WH	(4) 32W (BIPI)  	20.5	4	52.5	Matte White Acrylic Diffuser.
D	10847	OZ, SI	(4) 32W (BIPI) 	20	11.5	54	White Linen Acrylic Diffuser.

Measurements shown in inches.



D | 10697 WH



E | 10698 WH



F | 10315 WH



G | 10303 WH



H | 10304 WH



J | 10301 WH



K | 10839 WH

CEILING ENERGY EFFICIENT

	FLUOR. ITEM #	FINISH	FLUOR. BULB	W	H	L	EXT.	HCWO	NOTES
D	10697	WH	(2) 17W (BIPI) ✦ T24	26.5	6	---	4.5	3	Ⓧ May be installed on the wall or ceiling vertically or horizontally. White Acrylic Diffuser.
E	10698	WH	(2) 25W (BIPI) ✦ T24	38.5	6	---	4.5	3	Ⓧ May be installed on the wall or ceiling vertically or horizontally. White Acrylic Diffuser.
F	10315	WH	(2) 32W (BIPI) ✦ T24	9	3	48	---	---	Ⓧ Clear Prismatic Diffuser.
G	10303	WH	(4) 32W (BIPI) ✦ T24	16.75	5	51.5	---	---	Ⓧ White Architectural Acrylic Diffuser.
H	10304	WH	(4) 17W (BIPI) ✦ T24	27.5	4.5	28.5	---	---	Ⓧ White Architectural Acrylic Diffuser.
J	10301	WH	(2) 32W (BIPI) ✦ T24	11.25	4.75	51.5	---	---	Ⓧ White Architectural Acrylic Diffuser.
K	10839	WH	(2) 32W / 40W (T9, G10Q) ✦ T24	19	3.5	19	---	---	White Acrylic Diffuser.

Measurements shown in inches.



WALL SCONCES

VERSATILE & VERTICAL

The items on your walls say a lot about you. Minimalistic paintings? A collage of family photos? One dynamic print? Why not bring out the beauty in them all with a statement-making sconce (or two). Unique in design and uncommon in personality, Kichler sconces offer the scale and proportion needed to bring attention to a room without overtaking it. Flanking a picture or doorway...adorning a home theatre's every wall...or simply guiding you down a hallway: each fixture is a work of art all on its own.





MONA

CLASSIC PEWTER OR NATURAL BRASS FINISH
WITH SATIN ETCHED WHITE GLASS



A | 43375 CLP
Wall Sconce
ADA Compliant



A | 43375 NBR
Wall Sconce
ADA Compliant



B | 43376 CLP
Wall Sconce



B | 43376 NBR
Wall Sconce

MONA

	ITEM #	FINISH	INCAND. BULB	W	H	EXT.	HCWO	NOTES
A	43375	CLP, NBR	(2) 50W (G9) ✓ ⓘ	6.5	22	3.75	8.75	ⓘ
B	43376	CLP, NBR	(2) 50W (G9) ✓ ⓘ	8	30	4.5	12.25	

Measurements shown in inches. U.S. & Canada Patent Pending.

WALL SCONCES

ASSORTED FINISHES & GLASS



A | 43363 NBR
Alden



B | 43762 NI
Passport



C | 42203 NBR
Doncaster
ADA Compliant



D | 43787 NBR
City Loft™



D | 43787 OZ
City Loft™



D | 43787 PN
City Loft™

WALL SCONCES

	ITEM #	FINISH	INCAND. BULB	W	H	EXT.	HCWO	NOTES
A	43363	NBR	(1) 60W (C)	5	11.5	5.25	3.75	
B	43762	NI	(1) 60W (C)	5.5	16	4.25	12.75	Ⓜ (5-9W CFL) Satin Etched Cased Opal Glass.
C	42203	NBR	(3) 40W (C)	6.25	23	3.25	10.5	Ⓜ Two Tone Finish Natural Brass with Polished Nickel.
D	43787	NBR, OZ, PN	(1) 100W (M)	5.5	17.25	4.75	13	Ⓜ (23-30W CFL) White Opal Etched Glass.

Measurements shown in inches. U.S. & Canada Patent Pending.



WALL SCONCES

ASSORTED FINISHES & GLASS



A | 45086 PN
Freeport™
ADA Compliant



B | 45627 PN
Wall Sconce



C | 43910 CLP
Grayson



C | 43910 NBR
Grayson



D | 43934 NBR
Vance



E | 43777 AVI
Cahoon™

WALL SCONCES

ITEM #	FINISH	INCAND. BULB	W	H	EXT.	HCWO	NOTES
A	PN	(1) 60W (C)	7	17	3.75	4.5	♿ D Etched Linear Textured Glass.
B	PN	(1) 100W (M)	5	12	6	6	(23-30W CFL) Satin Etched Cased Opal Glass.
C	CLP, NBR	(1) 60W (C)	4.5	12.5	6	6.25	
D	NBR	(1) 60W (C)	6	16	6	8	Antique Mercury Glass.
E	AVI	(2) 60W (C) ✓	7.5	15	5.5	7.75	

Measurements shown in inches. U.S. & Canada Patent Pending.



WALL SCONCES

ASSORTED FINISHES & GLASS



A | 45580 NBR
Jasper



A | 45580 CH
Jasper



B | 45358 BPT
Granby™



B | 45358 CH
Granby™



B | 45358 OZ
Granby™



C | 42942 CLP
City Lights™

WALL SCONCES

ITEM #	FINISH	INCAND. BULB	W	H	EXT.	HCWO	NOTES
A 45580	CH, NBR	(1) 50W (G9)	4.5	11.5	5.75	5.75	Halogen light source. Satin Etched Cased Opal Glass.
B 45358	BPT, CH, OZ	(1) 100W (M)	5.75	14	7.5	7	(18-25W CFL) May be installed on wall with glass up or down. Satin Etched Cased Opal Glass.
C 42942	CLP	(2) 50W (G9)	15.5	16	4.5	7.25	Halogen light source. Satin Etched Cased Opal Glass.

Measurements shown in inches. U.S. & Canada Patent Pending.



WALL SCONCES

ASSORTED FINISHES & GLASS



A | 43825 WZC
Wall Sconce



B | 42126 OZ
Wall Sconce



C | 45161 OZ
Wall Sconce



C | 45161 AP
Wall Sconce



D | 6016 MBZ
Wall Sconce



E | 43756 AUB
Wall Sconce

WALL SCONCES

ITEM #	FINISH	INCAND. BULB	W	H	EXT.	HCWO	NOTES
A	WZC	(1) 60W (C)	4.75	18	7.5	5.5	
B	OZ	(1) 100W (M)	4.75	12.25	5.75	8	Ⓢ (23-30W CFL) Clear Seeded Glass.
C	AP, OZ	(1) 60W (C) Ⓢ	6	13	8.75	6.25	Ⓢ May be installed on wall with glass up or down. Krypton bulb included. OZ: Umber Etched Glass. AP: Satin Etched Cased Opal Glass.
D	MBZ	(1) 100 (M)	4.5	20.25	6.75	10.25	Ⓢ (23-30W CFL) May be installed on wall with glass up or down.
E	AUB	(2) 60W (M) ✓	7.5	12	5.5	6	Ⓢ (13-15W CFL) Auburn Stain Wood Elements with Brushed Nickel Finish and White Linen Shade.

Measurements shown in inches.



F | 45131 TRZ
Marchesa™



G | 43436 AUB
Colerne™



H | 43334 OZ
Kensington™




J | 43603 WZC
Industrial Cage

WALL SCONCES

ITEM #	FINISH	INCAND. BULB	W	H	EXT.	HCWO	NOTES
F	TRZ	(1) 60W (M) ✓	12.75	15	6.75	3.25	ⓓ (13-15W CFL) Piastra Glass.
G	AUB	(1) 100W (M)	8.75	14.75	9.5	7.25	ⓓ (23-30W CFL) Clear Seeded Glass.
H	OZ	(1) 60W (C)	5.25	13.5	7.5	9.25	ⓓ
J	WZC	(1) 100W (M)	5.5	12.25	7.25	2.5	ⓓ (23-30W CFL)

Measurements shown in inches. U.S. & Canada Patent Pending.



WALL SCONCES

ASSORTED FINISHES & GLASS



A | 43727 ESP
Piper



B | 42634 CH
Parker Point™



C | 43623 SGD
Abellona™



D | 43570 OZ
Casilda™



D | 43570 SGD
Casilda™



E | 45178 OZ
Leighton™

WALL SCONCES

	ITEM #	FINISH	INCAND. BULB	W	H	EXT.	HCWO	NOTES
A	43727	ESP	(2) 40W (C)	8	12.25	4	4.75	
B	42634	CH	(1) 60W (C)	6.75	15.5	8.5	10.25	Ⓛ Organza Shade.
C	43623	SGD	(2) 60W (C)	11.75	18	6	9.75	
D	43570	OZ, SGD	(1) 100W (M)	13.5	16	8.25	7.5	(18-25W CFL) Silver Beige Fabric Shade.
E	45178	OZ	(1) 60W (C/K)	8	14.75	9.75	8.75	Krypton or G Type bulb recommended. Off White Fabric Shade.

Measurements shown in inches. U.S. & Canada Patent Pending.



F | 43170 NI
Monroe™



F | 43170 OZ
Monroe™



G | 45421 OZ
Camerena™



G | 45421 NI
Camerena™



H | 43710 CLP
Emory



H | 43710 OZ
Emory



J | 45362 SWZ
Lara™



J | 45362 CLP
Lara™

WALL SCONCES

ITEM #	FINISH	INCAND. BULB	W	H	EXT.	HCWO	NOTES
F	43170 NI, OZ, SGD	(1) 100W (M)	6	14	9.25	8	☑ (23-30W CFL) May be installed on wall with glass up or down. Satin Etched Glass.
G	45421 NI, OZ	(1) 100W (M)	6	12.5	8.75	8.5	☑ (23-30W CFL) May be installed on wall with glass up or down. White Scavo and White Scavo with Light Umber Inside Tint Glass.
H	43710 CLP, OZ	(2) 60W (C)	8.5	15.5	5.25	9	☑ Clear Glass.
J	45362 CLP, SWZ	(1) 60W (C)	4.75	16.25	6	9.25	☑ Clear Glass with Inner Glass Drip Candle.

Measurements shown in inches. U.S. & Canada Patent Pending: H, J.



LED WALL SCONCES

Kichler® LED lighting exceeds the standards for reliability and beauty

Long-life light emitting diodes (LED) provide approx. 40,000-hour life span to L70 (70% initial lumens) – about 15 years of standard operation.

True optics: pure white light and controlled beam spread with no fade or drop off of light.

High Color Rendering Index (CRI)

Standard installation

LED OUTPUT

42372 NILED	800 INITIAL LUMENS, 20 WATTS, 3000 KELVIN, CRI 90, 40K LIFE
42943 CHLED	1200 INITIAL LUMENS, 30 WATTS, 3000 KELVIN, CRI 90, 40K LIFE
45604 CHLED	1200 INITIAL LUMENS, 30 WATTS, 3000 KELVIN, CRI 90, 40K LIFE
45656 CHLED	1200 INITIAL LUMENS, 30 WATTS, 3000 KELVIN, CRI 90, 40K LIFE
45615 OZLED/CHLED	1200 INITIAL LUMENS, 30 WATTS, 3000 KELVIN, CRI 90, 40K LIFE



A | 42372 NILED
Wall Sconce



B | 42943 CHLED
Wall Sconce

LED WALL SCONCES

ASSORTED FINISHES & GLASS



C | 45604 CHLED
Largo



D | 45656 CHLED
Trinsic™



E | 45615 OZLED
Landi™



E | 45615 CHLED
Wall Sconce



These devices
comply with part 15
of the FCC Regulations.

LED SCONCES

	LED ITEM #	FINISH	LIGHT SOURCE	W	H	EXT.	HCWO	NOTES
A	42372 NILED	NI	20W	5	12	3	6	White Glass.
B	42943 CHLED	CH	30W	5	13.5	4	6.75	Etched White Glass.
C	45604 CHLED	CH	30W	12	5	3.25	2.5	White Acrylic. Dimmable.
D	45656 CHLED	CH	30W	4.5	12	3.5	9	Satin Etched White Glass.
E	45615 OZLED / 45615 CHLED	CH, OZ	30W	12	5	2.75	2.5	White Glass.

Measurements shown in inches. U.S. & Canada Patent Pending.



SEDO™ LED

ARCHITECTURAL BRONZE™, PLATINUM
OR SATIN BLACK FINISH

LED OUTPUT

49492 AZ/PL/SBK	450 LUMENS, 16 WATTS 3000 KELVIN, CRI 80, 40K LIFE
49434 AZ/PL/SBK	800 LUMENS, 30 WATTS 3000 KELVIN, CRI 80, 40K LIFE
49435 AZ/PL/SBK	800 LUMENS, 30 WATTS 3000 KELVIN, CRI 80, 40K LIFE

Visit kichler.com for LED certification and testing updates.



A | 49492 AZ, PL, SBK
Indoor/Outdoor Sconce
ADA Compliant



B | 49434 AZ, PL, SBK
Indoor/Outdoor Sconce
ADA Compliant



C | 49435 AZ, PL, SBK
Indoor/Outdoor Sconce
ADA Compliant

CESYA™ LED

ARCHITECTURAL BRONZE™, PLATINUM
OR SATIN BLACK FINISH

LED OUTPUT

49494 AZ/PL/SBK	275 LUMENS, 16 WATTS 3000 KELVIN, CRI 80, 40K LIFE
49436 AZ/PL/SBK	550 LUMENS, 25 WATTS 3000 KELVIN, CRI 80, 40K LIFE
49437 AZ/PL/SBK	775 LUMENS, 30 WATTS 3000 KELVIN, CRI 80, 40K LIFE

Visit kichler.com for LED certification and testing updates.



D | 49494 AZ, PL, SBK
Indoor/Outdoor Sconce



E | 49436 AZ, PL, SBK
Indoor/Outdoor Sconce



F | 49437 AZ, PL, SBK
Indoor/Outdoor Sconce



These devices
comply with part 15
of the FCC Regulations.

SEDO™ LED

	LED ITEM #	FINISH	LIGHT SOURCE	W	H	EXT.	HCWO	NOTES
A	49492	AZ, PL, SBK	16W	6	12.25	4	6.25	Check Kichler.com website for certification and testing updates.
B	49434	AZ, PL, SBK	30W	6	18.25	4	9.25	Check Kichler.com website for certification and testing updates.
C	49435	AZ, PL, SBK	30W	6	24.25	4	12.25	Check Kichler.com website for certification and testing updates.

CESYA™ LED

	LED ITEM #	FINISH	LIGHT SOURCE	W	H	EXT.	HCWO	NOTES
D	49494	AZ, PL, SBK	16W	6	12	4.75	6	Check Kichler.com website for certification and testing updates.
E	49436	AZ, PL, SBK	25W	6	18	4.75	9	Check Kichler.com website for certification and testing updates.
F	49437	AZ, PL, SBK	30W	6	24	4.75	12	Check Kichler.com website for certification and testing updates.

Measurements shown in inches. U.S. & Canada Patent Pending.

WALL SCONCES ENERGY EFFICIENT

ASSORTED FINISHES & GLASS



Opal White
Acrylic Diffuser

A | **10448 OZ**
ADA Compliant



B | **10670 NI**
ADA Compliant



B | **10670 OZ**
ADA Compliant



Matte
White Acrylic
Diffuser

C | **10693 PN**
ADA Compliant

ENERGY EFFICIENT WALL SCONCES

	FLUOR. ITEM #	FINISH	FLUOR. BULB	W	H	L	EXT.	HCWO	NOTES
A	10448	OZ	(1) 24W (2G11)	5	21	4	4	16	Opal White Acrylic Glass.
B	10670	NI, OZ	(2) 13W (GU24)	5	16.5	---	4	8.25	OZ: Amber Linen Glass, NI: Satin Opal Glass.
C	10693	PN	(1) 18W (GU24)	5.75	12.5	---	4	6.25	Matte White Acrylic Glass.

Measurements shown in inches. U.S. & Canada Patent Pending.



WALL SCONCES

ENERGY EFFICIENT

ASSORTED FINISHES, GLASS & SHADES

Raye Fabric Shade
with Matte White
Acrylic Diffuser



A | 10796 SN
ADA Compliant

White Linen Fabric
Shade with Matte
White Acrylic Diffuser



B | 10438 NCH
Santiago
ADA Compliant


















C | 10439 NCH
Santiago
ADA Compliant

Natural Linen Fabric
Shade with Matte
White Acrylic Diffuser



D | 10421 SN
Rigel
ADA Compliant

ENERGY EFFICIENT SCONCES

	FLUOR. ITEM #	FINISH	FLUOR. BULB	W	H	EXT.	HCWO	NOTES
A	10796	SN	(2) 18W (GU24)  	16.25	8.25	4	3	  Raye Fabric Shade.
B	10438	NCH	(1) 13W (G24Q)  	5.5	14.25	3.75	5.25	  White Linen Fabric Shade.
C	10439	NCH	(2) 13W (G24Q)  	11	14.25	3.75	5.25	  White Linen Fabric Shade.
D	10421	SN	(1) 18W (GU24) 	12	10	4	5	  Natural Linen Fabric Shade.

Measurements shown in inches.



E | 10604 NI
Telford™



F | 10689 WH
ADA Compliant



G | 10333 WH
ADA Compliant



H | 10636 NI
10636 OZ
Wedgeport™



J | 10481 PC
Jervis™
ADA Compliant



K | 10686 PN
Freeport™
ADA Compliant

ENERGY EFFICIENT SCONCES

	FLUOR. ITEM #	FINISH	FLUOR. BULB	W	H	EXT.	HCWO	NOTES
E	10604	NI	(1) 13W (GU24)	7.5	12	9	6	May be installed on wall with glass up or down. Alabaster Swirl Glass.
F	10689	WH	(1) 18W (GU24)	9.75	8.75	3.75	4	Opal White Glass.
G	10333	WH	(1) 13W (G24Q)	16	8	3.5	3.25	
H	10636	NI, OZ	(1) 13W (GU24)	6.25	7.5	8	4.5	May be installed with glass up or down. Satin Etched Glass.
J	10481	PC	(1) 18W (GU24)	4.5	14.25	4	7	Etched White Opal Glass.
K	10686	PN	(1) 13W (GU24)	7	17	3.75	4.5	Clear Etched Linear Glass.

Measurements shown in inches.




WALL SCONCES ENERGY EFFICIENT

ASSORTED FINISHES & GLASS



A | **10630 PN**
Arcola
ADA Compliant



B | **10620 NI**
Nobu™
ADA Compliant



C | **10640 AZ**
Newport™
Indoor/Outdoor Wall
ADA Compliant



C | **10640 NI**
Newport™
Indoor/Outdoor Wall
ADA Compliant

ENERGY EFFICIENT SCONCES

	FLUOR. ITEM #	FINISH	FLUOR. BULB	W	H	EXT.	HCWO	NOTES
A	10630	PN	(1) 18W (GU24)	15	5.5	3.75	2.5	Matte White Acrylic Diffuser.
B	10620	NI	(2) 13W (G24Q)	13	9.5	4	5	Clear Outside Glass with White Inside.
C	10640	AZ, NI	(1) 18W (GU24)	9.25	10.25	3.75	5	White Acrylic Diffuser.

Measurements shown in inches.

WALL SCONCES

ASSORTED FINISHES & GLASS



D | 49061 OZ
Ripley™
Indoor/Outdoor Wall



E | 49060 OZ
Ripley™
Indoor/Outdoor Wall



F | 49059 OZ
Ripley™
Indoor/Outdoor Wall



G | 5359 NI
ADA Compliant



H | 6520 NI
ADA Compliant



J | 6521 NI
ADA Compliant



K | 9044 NI
Grenoble™
Indoor/Outdoor Wall

WALL SCONCES

ITEM #	FINISH	INCAND. BULB	W	H	EXTRA WIRE	EXT.	HCWO	NOTES
D	49061 OZ	(1) 40W (M)	12	10	---	13	3.25	☑ Dark Sky compliant with use of R14, 40W bulb.
E	49060 OZ	(1) 40W (M)	10	9	---	11.25	3	☑ Dark Sky compliant with use of R14, 40W bulb.
F	49059 OZ	(1) 40W (M)	8	7.5	---	9.25	2.5	☑ Dark Sky compliant with use of R14, 40W bulb.
G	5359 NI	(1) 100W (M)	4.75	9	---	6	4.5	ⓓ (9-13W CFL) May be installed on wall with glass up or down. Satin Etched Cased Opal Glass.
H	6520 NI	(1) 75W (M)	6	8	4	4	4	ⓓ NI: Alabaster Swirl Glass, TZ: Umber Mist Glass.
J	6521 NI	(1) 100W (M) ✓	6	10	5.75	4	6	ⓓ NI: Alabaster Swirl Glass, TZ: Umber Mist Glass.
K	9044 NI	(1) 150W (M)	11	8	---	11.5	2.5	☑

Measurements shown in inches. U.S. & Canada Patent Pending: D, E, F, G.



MIRRORS

REFLECTIVE & BEAUTIFUL

It's a secret interior designers often use: add a mirror to a room to fill it with reflected light. And no one knows lighting better than Kichler. Our mirror choices help you not only reflect the light, but also allows you to coordinate flawlessly with the other accessories in your room. From unique finishes to a range of shapes and sizes, you'll discover a Kichler® Mirror that enhances your room with brilliant style and substance.



A | 41096 NI



A | 41096 OZ



A | 41096 SGD



B | 41071 NI, OZ, SGD



C | 41011 CH, NBR, NI, OZ



D | 41067 CH
Pocelona™



E | 41056 NI
Structures™

MIRRORS

	ITEM #	FINISH	W	H	MIRROR SIZE	EXT.	NOTES
A	41096	NI, OZ, SGD	26.5	39	22 x 34	1	Eileen™ Beveled Mirror. Brushed Nickel, Olde Bronze® or Sterling Gold Frame.
B	41071	NI, OZ, SGD	24	30	21.25 x 27.25	---	Hendrik™ Beveled Mirror. Brushed Nickel, Olde Bronze® or Sterling Gold Frame.
C	41011	CH, NBR, NI, OZ	24	30	21 x 27	1.5	Beveled Mirror. Chrome, Distressed Black, Brushed Nickel or Olde Bronze® Frame. Mounts horizontal or vertical.
D	41067	CH	24	30	19.75 x 25.75	2.25	Pocelona™ Beveled Mirror.
E	41056	NI	24	30	21.75 x 29	0.75	Structures™ Beveled Mirror. Brushed Nickel.


Measurements shown in inches.




BATH & VANITY

PERSONAL & WELCOMING

Putting on makeup, brushing your teeth, unwinding at the end of the day. No room is more personal than the bath. Why not light it accordingly? From urban styles to traditional looks, our Bath & Vanity Collection has a lighting family ready to complement any style and enhance any task. Choose streamlined or embellished profiles, glistening crystal silhouettes or rich matte black options. Each offers a seemingly endless choice of lighting configurations that allows you to enjoy all the chaos of life beautifully.





NITA LED

POLISHED CHROME FINISH WITH
OPAL GLASS



These devices
comply with part 15
of the FCC Regulations.



A | **45820 CHLED**
ADA Compliant
NOT TO SCALE



B | **45821 CHLED**
ADA Compliant



C | **45822 CHLED**
ADA Compliant



D | **45823 CHLED**
ADA Compliant

LED OUTPUT

45820 CHLED	725 LUMENS, 14 WATTS, 51 LUMENS PER WATT, CRI 90, 3000 KELVIN, 40K LIFE
45821 CHLED	975 LUMENS, 20 WATTS, 50 LUMENS PER WATT, CRI 90, 3000 KELVIN, 40K LIFE
45822 CHLED	1350 LUMENS, 25 WATTS, 54 LUMENS PER WATT, CRI 90, 3000 KELVIN, 40K LIFE
45823 CHLED	1400 LUMENS, 30 WATTS, 46 LUMENS PER WATT, CRI 90, 3000 KELVIN, 40K LIFE

*Delivered Lumens. Visit kichler.com for recent performance and certification data.

NITA LED

	LED ITEM #	FINISH	LIGHT SOURCE	W	H	EXT.	HCWO	NOTES
A	45820 CHLED	CH	14W	13	4.75	3.5	2.25	May be installed on wall vertically or horizontally. Dimmable.
B	45821 CHLED	CH	20W	19	4.75	3.5	2.25	May be installed on wall vertically or horizontally. Dimmable.
C	45822 CHLED	CH	25W	25.25	4.75	3.5	2.25	May be installed on wall vertically or horizontally. Dimmable.
D	45823 CHLED	CH	30W	31.25	4.75	3.5	2.25	May be installed on wall vertically or horizontally. Dimmable.

Measurements shown in inches. U.S. & Canada Patent Pending.



These devices
comply with part 15
of the FCC Regulations.

TRINSIC™ LED

POLISHED CHROME FINISH WITH
SATIN ETCHED WHITE GLASS



A | 45657 CHLED
ADA Compliant



C | 45656 CHLED
Wall Sconce
ADA Compliant
NOT TO SCALE



B | 45658 CHLED
ADA Compliant

LED OUTPUT

45657 CHLED	1200 LUMENS*, 30 WATTS, 3000 KELVIN, CRI 90, 40K LIFE
45658 CHLED	2400 LUMENS*, 60 WATT, 3000 KELVIN, CRI 90, 40K LIFE
45656 CHLED	3600 LUMENS*, 90 WATT, 3000 KELVIN, CRI 90, 40K LIFE

Visit kichler.com for recent performance and certification data.

TRINSIC™ LED

	LED ITEM #	FINISH	LIGHT SOURCE	W	H	L	EXT.	HCWO	NOTES
A	45657 CHLED	CH	(2) 60W	22	4.5	3.5	3.5	2.25	May be installed on the wall vertically or horizontally. Dimmable.
B	45658 CHLED	CH	(3) 90W	32	4.5	3.5	3.5	2.25	May be installed on the wall vertically or horizontally. Dimmable.
C	45656 CHLED	CH	(1) 30W	12	4.5	---	3.5	9	Dimmable.

Measurements shown in inches. U.S. & Canada Patent Pending.

ZOLON LED

POLISHED CHROME FINISH WITH
SATIN ETCHED WHITE GLASS



A | **45828 CHLED**
ADA Compliant



B | **45829 CHLED**
ADA Compliant



C | **45830 CHLED**
ADA Compliant



D | **45831 CHLED**
ADA Compliant



These devices
comply with part 15
of the FCC Regulations.

Visit kichler.com for recent
performance and certification data.

ZOLON LED

	LED ITEM #	FINISH	LIGHT SOURCE	W	H	EXT.	HCWO	NOTES
A	45828 CHLED	CH	14W	12.25	5	3.75	2.5	May be installed on wall vertically or horizontally. Dimmable.
B	45829 CHLED	CH	19W	18	5	3.75	2.5	May be installed on wall vertically or horizontally. Dimmable.
C	45830 CHLED	CH	27W	24	5	3.75	2.5	May be installed on wall vertically or horizontally. Dimmable.
D	45831 CHLED	CH	30W	30	5	3.75	2.5	May be installed on wall vertically or horizontally. Dimmable.

Measurements shown in inches. U.S. & Canada Patent Pending.

ZOLON LED

OLDE BRONZE® FINISH WITH
SATIN ETCHED WHITE GLASS



A | **45829 OZLED**
ADA Compliant




D | **45828 OZLED**
ADA Compliant



B | **45830 OZLED**
ADA Compliant



C | **45831 OZLED**
ADA Compliant



These devices
comply with part 15
of the FCC Regulations.

LED OUTPUT

45828 CHLED/ OZLED	675 LUMENS, 14 WATTS, 48 LUMENS PER WATT, 3000 KELVIN, CRI 90, 40K LIFE
45829 CHLED/ OZLED	925 LUMENS*, 20 WATTS, 47 LUMENS PER WATT, 3000 KELVIN, CRI 90, 40K LIFE
45830 CHLED/ OZLED	1250 LUMENS*, 25 WATT, 49 LUMENS PER WATT, 3000 KELVIN, CRI 90, 40K LIFE
45831 CHLED/ OZLED	1450 LUMENS, 30 WATTS, 48 LUMENS PER WATT, 3000 KELVIN, CRI 90, 40K LIFE

*Delivered Lumens. * Visit kichler.com for recent performance and certification data.

ZOLON LED

	LED ITEM #	FINISH	LIGHT SOURCE	W	H	EXT.	HCWO	NOTES
A	45829 OZLED	OZ	19W	18	5	3.75	2.5	May be installed on wall vertically or horizontally. Dimmable.
B	45830 OZLED	OZ	27W	24	5	3.75	2.5	May be installed on wall vertically or horizontally. Dimmable.
C	45831 OZLED	OZ	30W	30	5	3.75	2.5	May be installed on wall vertically or horizontally. Dimmable.
D	45828 OZLED	OZ	14W	12.25	5	3.75	2.5	May be installed on wall vertically or horizontally. Dimmable.

Measurements shown in inches. U.S. & Canada Patent Pending.

CONTESSA LED

POLISHED CHROME FINISH WITH SATIN ETCHED
WHITE GLASS & FRETWORK DETAILING



These devices
comply with part 15
of the FCC Regulations.



A | 45851 CHLED
Wall Sconce
ADA Compliant
NOT TO SCALE



B | 45852 CHLED
ADA Compliant



C | 45853 CHLED



D | 45854 CHLED

LED OUTPUT

45851 CHLED	1200 LUMENS*, 14 WATT, 3000 KELVIN, CRI 90, 40K LIFE
45852 CHLED	1800 LUMENS*, 20 WATT, 3000 KELVIN, CRI 90, 40K LIFE
45853 CHLED	2400 LUMENS*, 25 WATT, 3000 KELVIN, CRI 90, 40K LIFE
45854 CHLED	3000 LUMENS*, 30 WATT, 3000 KELVIN, CRI 90, 40K LIFE

Visit kichler.com for recent performance
and certification data.

CONTESSA LED

	LED ITEM #	FINISH	LIGHT SOURCE	W	H	EXT.	HCWO	NOTES
A	45851 CHLED	CH	(2) 14W	12	5	3.25	6	May be installed on wall vertically or horizontally. Dimmable.
B	45852 CHLED	CH	(2) 20W	18	5	3.75	9	May be installed on wall vertically or horizontally. Dimmable.
C	45853 CHLED	CH	(4) 25W	24	5	4.25	12	May be installed on wall vertically or horizontally. Dimmable.
D	45854 CHLED	CH	(4) 30W	30	5	4.5	15	May be installed on wall vertically or horizontally. Dimmable.

Measurements shown in inches. U.S. & Canada Patent Pending.

CONTESSA

POLISHED CHROME FINISH WITH SATIN ETCHED
CASED OPAL GLASS & FRETWORK DETAILING



A | 45559 CH



B | 45560 CH



C | 45561 CH



D | 45558 CH
Wall Sconce
NOT TO SCALE

CONTESSA

ITEM #	FINISH	INCAND. BULB	W	H	EXT.	HCWO	NOTES	
A	45559	CH	(2) 100W (M)	11.25	6.75	5.25	4.25	Ⓧ (23-30W CFL)
B	45560	CH	(3) 100W (M)	18.5	6.75	5.25	4.25	Ⓧ (23-30W CFL)
C	45561	CH	(4) 100W (M)	26	6.75	5.25	4.25	Ⓧ (23-30W CFL)
D	45558	CH	(1) 100W (M)	5	7	5.25	3.5	Ⓧ (23-30W CFL)

Measurements shown in inches. U.S. & Canada Patent Pending.

LANDI LED

POLISHED CHROME FINISH WITH WHITE GLASS



A | 45615 CHLED
Wall Sconce
ADA Compliant
NOT TO SCALE



B | 45617 CHLED
ADA Compliant



C | 45618 CHLED
ADA Compliant



These devices
comply with part 15
of the FCC Regulations.

LED OUTPUT

45615 CHLED	1200 LUMENS*, 30 WATTS, 3000 KELVIN, CRI 90, 40K LIFE
45617 CHLED	2400 LUMENS*, 60 WATT, 3000 KELVIN, CRI 90, 40K LIFE
45618 CHLED	3600 LUMENS*, 90 WATT, 3000 KELVIN, CRI 90, 40K LIFE

Visit kichler.com for recent performance
and certification data.

LANDI LED

	LED ITEM #	FINISH	LIGHT SOURCE	W	H	EXT.	HCWO	NOTES
A	45615 CHLED	CH	(1) 30W	12	5	2.75	2.5	ⓓ Ⓞ May be installed on wall vertically or horizontally. Dimmable.
B	45617 CHLED	CH	(2) 60W	24	5	2.75	2.5	ⓓ Ⓞ May be installed on wall vertically or horizontally. Dimmable.
C	45618 CHLED	CH	(3) 90W	36	5	3.25	2.5	ⓓ Ⓞ May be installed on wall vertically or horizontally. Dimmable.

Measurements shown in inches. U.S. & Canada Patent Pending.

LANDI LED

OLDE BRONZE® FINISH WITH WHITE GLASS



C | 45615 OZLED
Wall Sconce
ADA Compliant
NOT TO SCALE



A | 45617 OZLED
ADA Compliant



B | 45618 OZLED
ADA Compliant



These devices
comply with part 15
of the FCC Regulations.

LANDI LED

	LED ITEM #	FINISH	LIGHT SOURCE	W	H	L	EXT.	HCWO	NOTES
A	45617 OZLED	OZ	(2) 60W	24	5	---	2.75	2.5	ⓓ Ⓞ May be installed on wall vertically or horizontally. Dimmable.
B	45618 OZLED	OZ	(3) 90W	36	5	---	2.75	2.5	ⓓ Ⓞ May be installed on wall vertically or horizontally. Dimmable.
C	45615 OZLED	OZ	(1) 30W	12	5	12	2.75	2.5	ⓓ Ⓞ May be installed on wall vertically or horizontally. Dimmable.

Measurements shown in inches. U.S. & Canada Patent Pending.

FREEPORT™ LED

POLISHED NICKEL FINISH WITH
ETCHED LINEAR TEXTURED GLASS



These devices
comply with part 15
of the FCC Regulations.

MATCHING COLLECTION

See entire Freeport™
Collection on
page 424.



LED OUTPUT

45087 PNLED	1200 LUMENS*, 30 WATTS, 3000 KELVIN, CRI 90, 40K LIFE
42091 PNLED	2000 LUMENS*, 50 WATT, 3000 KELVIN, CRI 90, 40K LIFE
45088 PNLED	2400 LUMENS*, 60 WATT, 3000 KELVIN, CRI 90, 40K LIFE

Visit kichler.com for recent performance
and certification data.

MULTI- POSITIONAL WALL SCONCE

Create two distinct lighting
options in one.



A | 45087 PNLED
ADA Compliant



B | 42091 PNLED



C | 45088 PNLED

FREEPORT™ LED

	LED ITEM #	FINISH	LIGHT SOURCE	W	H	EXT.	HCWO	NOTES
A	45087 PNLED	PN	(1) 30W	22	5	3.75	1.84	May be installed on wall vertically or horizontally. Dimmable.
B	42091 PNLED	PN	(2) 50W	28	5	4.75	---	May be installed on wall vertically or horizontally. Dimmable.
C	45088 PNLED	PN	(2) 60W	36	5	4.25	1.84	May be installed on wall vertically or horizontally. Dimmable.

Measurements shown in inches. U.S. & Canada Patent Pending.

FREEPORT™

POLISHED NICKEL FINISH WITH
ETCHED LINEAR TEXTURED GLASS

MULTI-POSITIONAL WALL SCONCE

Create two distinct lighting options with
one fixture: fixture can be installed on the wall
horizontally or vertically.

B | 45087 PN
Linear Bath
ADA Compliant



A | 45086 PN
10686 PN
Wall Sconce
ADA Compliant



C | 42091 PN
Linear Bath














D | 45088 PN
Linear Bath

MATCHING BATH

See matching LED
bath fixtures
on page 425.



FREEPORT™

ITEM #	FLUOR. ITEM #	FINISH	INCAND. BULB	FLUOR. BULB	W	H	EXT.	HCWO	NOTES
A	45086 10686	PN	(1) 60W (C)	(1) 13W (GU24)  	7	17	3.75	4.5	 
B	45087	PN	(2) 60W (C/K) 	---	22	5	3.75	2.5	  May be installed on wall vertically or horizontally. Krypton bulb included.
C	42091	PN	(2) 60W (C/K) 	---	28	5	4.75	2.5	 May be installed on wall vertically or horizontally. Krypton light source.
D	45088	PN	(4) 60W (C/K) 	---	36	5	4.25	2.5	 May be installed on wall vertically or horizontally. Krypton bulb included.

Measurements shown in inches. U.S. & Canada Patent Pending.

IMPELLO LED

OLDE BRONZE® FINISH OR
POLISHED CHROME FINISH WITH
SATIN ETCHED WHITE GLASS



A | 45836 CHLED, OZLED
ADA Compliant



B | 45801 CHLED, OZLED
ADA Compliant



C | 45838 CHLED, OZLED
ADA Compliant



These devices
comply with part 15
of the FCC Regulations.



D | 45839 CHLED, OZLED
ADA Compliant

LED OUTPUT

45836 CHLED/ OZLED	625 LUMENS*, 14 WATTS, 45 LUMENS PER WATT, 3000 KELVIN, CRI 90, 40K LIFE
45801 CHLED/ OZLED	900 LUMENS*, 20 WATTS, 45 LUMENS PER WATT, 3000 KELVIN, CRI 90, 40K LIFE
45838 CHLED/ OZLED	1200 LUMENS*, 26 WATTS, 46 LUMENS PER WATT, 3000 KELVIN, CRI 90, 40K LIFE
45839 CHLED/ OZLED	1275 LUMENS*, 30 WATTS, 43 LUMENS PER WATT, 3000 KELVIN, CRI 90, 40K LIFE

*Initial Lumens. Visit kichler.com for recent performance and certification data.

IMPELLO LED

	ITEM #	FINISH	LIGHT SOURCE	W	H	EXT.	HCWO	NOTES
A	45836 CHLED / 45836 OZLED	CH, OZ	14W	12.25	5.5	3.5	2.75	May be installed on wall vertically or horizontally. Dimmable.
B	45801 CHLED / 45801 OZLED	CH, OZ	20W	18.25	5.5	3.5	2.75	May be installed on wall vertically or horizontally. Dimmable.
C	45838 CHLED / 45838 OZLED	CH, OZ	26W	24.25	5.5	3.5	2.75	May be installed on wall vertically or horizontally. Dimmable.
D	45839 CHLED / 45839 OZLED	CH, OZ	30W	30.25	5.5	3.5	2.75	May be installed on wall vertically or horizontally. Dimmable.

Measurements shown in inches. U.S. & Canada Patent Pending.

TORI LED


POLISHED CHROME FINISH WITH
SATIN ETCHED WHITE GLASS



A | 45844 CHLED



B | 45845 CHLED



C | 45846 CHLED



D | 45847 CHLED

LED OUTPUT

45844 CHLED	575 LUMENS*, 14 WATTS, 41 LUMENS PER WATT, 3000 KELVIN, CRI 90, 40K LIFE
45845 CHLED	975 LUMENS*, 20 WATTS, 48 LUMENS PER WATT, 3000 KELVIN, CRI 90, 40K LIFE
45846 CHLED	1250 LUMENS*, 25 WATTS, 50 LUMENS PER WATT, 3000 KELVIN, CRI 90, 40K LIFE
45847 CHLED	1400 LUMENS*, 30 WATTS, 46 LUMENS PER WATT, 3000 KELVIN, CRI 90, 40K LIFE

*Initial Lumens. Visit kichler.com for recent performance and certification data.

TORI LED

	LED ITEM #	FINISH	LIGHT SOURCE	W	H	EXT.	HCWO	NOTES
A	45844 CHLED	CH	14W	12.25	5	4.25	2.5	D May be installed on wall vertically or horizontally. Dimmable.
B	45845 CHLED	CH	20W	18.25	5	4.25	2.5	D May be installed on wall vertically or horizontally. Dimmable.
C	45846 CHLED	CH	20W	24.25	5	4.25	2.5	D May be installed on wall vertically or horizontally. Dimmable.
D	45847 CHLED	CH	30W	30.25	5	4.25	2.5	D May be installed on wall vertically or horizontally. Dimmable.

Measurements shown in inches. U.S. & Canada Patent Pending.

LARGO LED

POLISHED CHROME FINISH WITH WHITE ACRYLIC



A | **45604 CHLED**
Wall Sconce
ADA Compliant
NOT TO SCALE



B | **45605 CHLED**
ADA Compliant



C | **45606 CHLED**
ADA Compliant



These devices
comply with part 15
of the FCC Regulations.

LED OUTPUT

45604 CHLED	1200 LUMENS*, 30 WATTS, 3000 KELVIN, CRI 90, 40K LIFE
45605 CHLED	2400 LUMENS*, 60 WATT, 3000 KELVIN, CRI 90, 40K LIFE
45606 CHLED	3600 LUMENS*, 90 WATT, 3000 KELVIN, CRI 90, 40K LIFE

Visit kichler.com for recent performance and certification data.

LARGO LED

	LED ITEM #	FINISH	LIGHT SOURCE	W	H	EXT.	HCWO	NOTES
A	45604 CHLED	CH	(1) 30W	12	5	3.25	2.5	May be installed on the wall vertically or horizontally. Dimmable.
B	45605 CHLED	CH	(2) 60W	24	5	3.25	2.5	May be installed on the wall vertically or horizontally. Dimmable.
C	45606 CHLED	CH	(3) 90W	36	5	3.25	2.5	May be installed on the wall vertically or horizontally. Dimmable.

Measurements shown in inches. U.S. & Canada Patent Pending.

JARDINE

POLISHED CHROME FINISH WITH
SATIN ETCHED GLASS & CRYSTAL ACCENTS

MULTI-POSITIONAL WALL SCONCE

Create two distinct lighting options with
one fixture: fixture can be installed on the wall
horizontally or vertically.

A | 45291 CH



45291 CH Shown Vertically as
Wall Sconce



45291 CH Shown Horizontally
as Linear Bath

Satin Etched
Glass Diffuser
with Decorative
Crystal



B | 45293 CH

MATCHING COLLECTION

See entire Jardine
Collection on
page 224-225.



JARDINE

	ITEM #	FINISH	INCAND. BULB	W	H	EXT.	HCWO	NOTES
A	45291	CH	(2) 50W (G9)	25	4.5	4.25	2.25	Halogen light source. May be installed on wall vertically or horizontally.
B	45293	CH	(4) 50W (G9)	36.5	4.5	4.25	2.25	Halogen light source. May be installed on wall vertically or horizontally.

Measurements shown in inches. U.S. & Canada Patent Pending.

MILLWRIGHT™

DISTRESSED ANTIQUE GREY WOOD FINISH WITH
MATTE BLACK ACCENTS & CLEAR SEEDED GLASS



A | 45542 DAG
Wall Sconce
NOT TO SCALE



B | 45543 DAG



C | 45544 DAG



D | 45545 DAG



VINTAGE
FILAMENT
BULB

SOLD SEPARATELY
60W Medium Base
4071 CLR

MILLWRIGHT™

ITEM #	FINISH	INCAND. BULB	W	H	EXT.	HCWO	NOTES	
A	45542	DAG	(1) 100W (M)	5.5	9	5	4.5	Ⓧ May be installed with glass up or down.
B	45543	DAG	(2) 100W (M)	14	7.75	5	5.25	Ⓧ May be installed with glass up or down.
C	45544	DAG	(3) 100W (M)	22	7.75	5	5.25	Ⓧ May be installed with glass up or down.
D	45545	DAG	(4) 100W (M)	29.5	7.75	5	5.25	Ⓧ May be installed with glass up or down.

Measurements shown in inches. U.S. & Canada Patent Pending.

BRAELYN™

OLDE BRONZE® FINISH WITH
CLEAR SEEDED GLASS



A | 45457 OZ
Wall Sconce
NOT TO SCALE



B | 45458 OZ



C | 45459 OZ



D | 45460 OZ

BRAELYN™

ITEM #	FINISH	INCAND. BULB	W	H	EXT.	HCWO	NOTES
A	OZ	(1) 60W (M) A19 / 60W S21	5	9.5	5.75	6	⓪ (13-15W CFL)
B	OZ	(2) 100W (M) A19 / 60W S21	15	10	5.75	2.25	⓪ (23-30W CFL)
C	OZ	(3) 100W (M) A19 / 60W S21	24	10	7.25	2.25	⓪ (23-30W CFL)
D	OZ	(4) 100W (M) A19 / 60W S21	34.25	10	7.25	2.25	⓪ (23-30W CFL)

Measurements shown in inches. U.S. & Canada Patent Pending.



Braelyn™ Wall Sconce 45457 CH & 2 Light Bath 45458 CH | Page 433



VINTAGE
FILAMENT
BULB

SOLD SEPARATELY
60W Medium Base
4071 CLR

BRAELYN™

POLISHED CHROME FINISH WITH
CLEAR SEEDED GLASS



A | 45457 CH
Wall Sconce
NOT TO SCALE



B | 45458 CH



C | 45459 CH

Clear Seeded Glass



D | 45460 CH

BRAELYN™

	ITEM #	FINISH	INCAND. BULB	W	H	EXT.	HCWO	NOTES
A	45457	CH	(1) 60W (M) A19 / 60W S21	5	9.5	5.75	6	Ⓟ (13-15W CFL)
B	45458	CH	(2) 100W (M) A19 / 60W S21	15	10	5.75	2.25	Ⓟ (23-30W CFL)
C	45459	CH	(3) 100W (M) A19 / 60W S21	24	10	7.25	2.25	Ⓟ (23-30W CFL)
D	45460	CH	(4) 100W (M) A19 / 60W S21	34.25	10	7.25	2.25	Ⓟ (23-30W CFL)

Measurements shown in inches. U.S. & Canada Patent Pending.

SIGNATA™

NATURAL BRASS FINISH WITH
CLEAR CURVED GLASS PANELS



A | 45701 NBR
Wall Sconce
ADA Compliant
NOT TO SCALE



B | 45702 NBR



C | 45703 NBR



D | 45704 NBR



VINTAGE FILAMENT BULB

SOLD SEPARATELY
40W Candelabra Base
5971 CLR

SIGNATA™

ITEM #	FINISH	INCAND. BULB	W	H	EXT.	HCWO	NOTES
A	NBR	(1) 60W (C) B Type / 40W T Type	5.75	8	4	4.25	Ⓟ Ⓡ
B	NBR	(2) 60W (C) B Type / 40W T Type	16	7.5	4.5	4.75	Ⓟ
C	NBR	(3) 60W (C) B Type / 40W T Type	24	7.5	4.75	4.75	Ⓟ
D	NBR	(4) 60W (C) B Type / 40W T Type	30	7.5	4.75	4.75	Ⓟ

Measurements shown in inches. U.S. & Canada Patent Pending.

SIGNATA™

CLASSIC PEWTER FINISH WITH
CLEAR CURVED GLASS PANELS



A | 45702 CLP



B | 45703 CLP



C | 45704 CLP



D | 45701 CLP
Wall Sconce
ADA Compliant
NOT TO SCALE

SIGNATA™

	ITEM #	FINISH	INCAND. BULB	W	H	EXT.	HCWO	NOTES
A	45702	CLP	(2) 60W (C) B Type / 40W T Type	16	7.5	4.5	4.75	D
B	45703	CLP	(3) 60W (C) B Type / 40W T Type	24	7.5	4.75	4.75	D
C	45704	CLP	(4) 60W (C) B Type / 40W T Type	30	7.5	4.75	4.75	D
D	45701	CLP	(1) 60W (C) B Type / 40W T Type	5.75	8	4	4.25	D 5

Measurements shown in inches. U.S. & Canada Patent Pending.

JASPER

POLISHED CHROME FINISH WITH
SATIN ETCHED CASED OPAL GLASS



A | 45580 CH
Wall Sconce
NOT TO SCALE



B | 45581 CH



C | 45582 CH



D | 45583 CH

JASPER

ITEM #	FINISH	INCAND. BULB	W	H	EXT.	HCWO	NOTES
A	CH	(1) 50W (G9)	4.5	11.5	5.75	5.75	
B	CH	(2) 50W (G9)	16.5	7.75	6	5.5	
C	CH	(3) 50W (G9)	24.5	7.75	6	5.5	
D	CH	(4) 50W (G9)	32.25	7.5	6	5.5	

Measurements shown in inches. U.S. & Canada Patent Pending.

JASPER

NATURAL BRASS FINISH WITH
SATIN ETCHED CASED OPAL GLASS



A | 45581 NBR



B | 45582 NBR



C | 45583 NBR



D | 45580 NBR
Wall Sconce
NOT TO SCALE

JASPER

ITEM #	FINISH	INCAND. BULB	W	H	EXT.	HCWO	NOTES	
A	45581	NBR	(2) 50W (G9)	16.5	7.75	6	5.5	
B	45582	NBR	(3) 50W (G9)	24.5	7.75	6	5.5	
C	45583	NBR	(4) 50W (G9)	32.25	7.5	6	5.5	
D	45580	NBR	(1) 50W (G9)	4.5	11.5	6	5.5	

Measurements shown in inches. U.S. & Canada Patent Pending.

CALLEIGH™

BRUSHED NICKEL FINISH WITH
SATIN ETCHED CASED OPAL GLASS



A | 45117 NI
Wall Sconce
NOT TO SCALE



B | 45118 NI



C | 45119 NI



D | 45120 NI



E | 45190 NI

MATCHING MIRROR

41056 NI
See page 413 or
kichler.com.



CALLEIGH™

ITEM #	FINISH	INCAND. BULB	W	H	EXT.	HCWO	NOTES	
A	45117	NI	(1) 100W (M)	6	8	7.25	4.5	Ⓟ (18-25W CFL) May be installed with glass up or down.
B	45118	NI	(2) 100W (M)	16	8	7	5.5	Ⓟ (18-25W CFL) May be installed with glass up or down.
C	45119	NI	(3) 100W (M)	26	8.5	7	2.5	Ⓟ (18-25W CFL) May be installed with glass up or down.
D	45120	NI	(4) 100W (M)	34.5	9	7	2.5	Ⓟ (18-25W CFL) May be installed with glass up or down.
E	45190	NI	(5) 100W (M)	46	9.5	7	2.5	Ⓟ (18-25W CFL) May be installed with glass up or down.

Measurements shown in inches.

HENDRIK™

POLISHED CHROME FINISH WITH SATIN ETCHED CASED OPAL GLASS



A | 5077 CH



B | 5078 CH



C | 5079 CH



D | 5085 CH



E | 7772 CH
Directional Rail Light



F | 5076 CH
Wall Sconce
NOT TO SCALE

HENDRIK™

ITEM #	FINISH	INCAND. BULB	W	H	L	EXT.	HCWO	NOTES	
A	5077	CH	(2) 100W (M)	14.5	7.75	---	6.5	5.5	Ⓛ (18-25W CFL) May be installed with glass up or down.
B	5078	CH	(3) 100W (M)	24	7.75	---	6.5	5.5	Ⓛ (18-25W CFL) May be installed with glass up or down.
C	5079	CH	(4) 100W (M)	33.75	7.75	---	6.5	5.5	Ⓛ (18-25W CFL) May be installed with glass up or down.
D	5085	CH	(5) 100W (M)	43	7.75	---	6.5	5.25	Ⓛ (18-25W CFL) May be installed with glass up or down.
E	7772	CH	(4) 50W (GU10)	5	8.25	30	6.25	2.5	Ⓛ
F	5076	CH	(1) 100W (M)	5.5	12	---	8	6	Ⓛ (18-25W CFL) May be installed with glass up or down.

Measurements shown in inches. U.S. Design Patent No. D688,828: A,B,C,F. U.S. & Canada Patent Pending: D & E.

HENDRIK™

BRUSHED NICKEL FINISH WITH
SATIN ETCHED CASED OPAL GLASS



A | 5076 NI
Wall Sconce
NOT TO SCALE



B | 5077 NI



C | 5078 NI



D | 5079 NI



E | 5085 NI



F | 7772 NI
Directional Rail Light

MATCHING MIRROR

41071 NI
See page 413 or
kichler.com.



MATCHING COLLECTION

See entire Hendrik™
Collection on
pages 207-209.



HENDRIK™

ITEM #	FINISH	INCAND. BULB	W	H	L	EXT.	HCWO	NOTES	
A	5076	NI	(1) 100W (M)	5.25	12	---	8	6	ⓓ (18-25W CFL) May be installed with glass up or down.
B	5077	NI	(2) 100W (M)	14.5	7.75	---	6.5	5.5	ⓓ (18-25W CFL) May be installed with glass up or down.
C	5078	NI	(3) 100W (M)	24	7.75	---	6.5	5.5	ⓓ (18-25W CFL) May be installed with glass up or down.
D	5079	NI	(4) 100W (M)	33.75	7.75	---	6.5	5.5	ⓓ (18-25W CFL) May be installed with glass up or down.
E	5085	NI	(5) 100W (M)	43	7.75	---	6.5	5.25	ⓓ (18-25W CFL) May be installed with glass up or down.
F	7772	NI	(4) 50W GU10	5	8.25	30	6.25	2.5	ⓓ

Measurements shown in inches. U.S. Design Patent No. D688,828: A,B,C,F. U.S. & Canada Patent Pending: D & E.

MATCHING MIRROR

41071 OZ
See page 413 or
kichler.com.



A | 5077 OZ



B | 5078 OZ



C | 5079 OZ



D | 5085 OZ



E | 7772 OZ
Directional Rail Light

HENDRIK™

OLDE BRONZE® FINISH WITH
LIGHT UMBER GLASS



F | 5076 OZ
Wall Sconce
NOT TO SCALE

MATCHING COLLECTION

See entire Hendrik™
Collection on
pages 204-206.



HENDRIK™

ITEM #	FINISH	INCAND. BULB	W	H	L	EXT.	HCWO	NOTES	
A	5077	OZ	(2) 100W (M)	14.5	7.75	---	6.5	5.5	Ⓧ (18-25W CFL) May be installed with glass up or down.
B	5078	OZ	(3) 100W (M)	24	7.75	---	6.5	5.5	Ⓧ (18-25W CFL) May be installed with glass up or down.
C	5079	OZ	(4) 100W (M)	33.75	7.75	---	6.5	5.5	Ⓧ (18-25W CFL) May be installed with glass up or down.
D	5085	OZ	(5) 100W (M)	43	7.75	---	6.5	5.25	Ⓧ (18-25W CFL) May be installed with glass up or down.
E	7772	OZ	(4) 50W GU10	5	8.25	30	6.25	2.5	Ⓧ Halogen Light Source.
F	5076	OZ	(1) 100W (M)	5.25	12	---	8	6	Ⓧ (18-25W CFL) May be installed with glass up or down.

Measurements shown in inches. U.S. Design Patent No. D688,828: A,B,C,F. U.S. & Canada Patent Pending: D & E.

SOULDERN

MARBLED BRONZE FINISH WITH DISTRESSED
UMBER ETCHED GLASS



A | 6016 MBZ
Wall Sconce
NOT TO SCALE



B | 5315 MBZ



C | 5316 MBZ



D | 5317 MBZ

SOULDERN

ITEM #	FINISH	INCAND. BULB	W	H	EXT.	HCWO	NOTES	
A	6016	MBZ	(1) 100 (M)	4.5	20.25	6.75	10.25	Ⓧ (23-30W CFL) May be installed on wall with glass up or down.
B	5315	MBZ	(2) 100 (M)	15.75	9.5	6.5	7.25	Ⓧ (23-30W CFL) May be installed on wall with glass up or down.
C	5316	MBZ	(3) 100 (M)	23.5	9.5	6.5	7.25	Ⓧ (23-30W CFL) May be installed on wall with glass up or down.
D	5317	MBZ	(4) 100 (M)	30	9.5	6.5	2.25	Ⓧ (23-30W CFL) May be installed on wall with glass up or down.

Measurements shown in inches.

URBAN ICE™

ANTIQUE PEWTER FINISH & CLEAR POLISHED EXTERIOR GLASS WITH INSIDE ETCH OR OLDE BRONZE® FINISH & CLEAR POLISHED EXTERIOR GLASS WITH INSIDE UMBER ETCH



A | 5460 AP, OZ



B | 5461 AP, OZ



C | 5462 AP, OZ



D | 5459 AP, OZ
Wall Sconce
NOT TO SCALE

MATCHING MIRROR

41011 OZ
See page 513 or
kichler.com.



URBAN ICE™

	ITEM #	FINISH	INCAND. BULB	W	H	EXT.	HCWO	NOTES
A	5460	AP, OZ	(2) 100W (M)	12.5	6.25	6.75	3.25	Ⓧ May be installed on wall with glass up or down.
B	5461	AP, OZ	(3) 100W (M)	19.5	6.25	6.75	3	Ⓧ May be installed on wall with glass up or down.
C	5462	AP, OZ	(4) 100W (M)	26.75	6.25	6.75	3.25	Ⓧ May be installed on wall with glass up or down.
D	5459	AP, OZ	(1) 100W (M)	4.5	8	6.75	4	Ⓧ May be installed on wall with glass up or down.

Measurements shown in inches.



CASILDA™

OLDE BRONZE™ FINISH WITH OPTICAL CRYSTAL ACCENTS & SATIN ETCHED CASED OPAL GLASS



A | 45371 OZ
Wall Sconce
NOT TO SCALE



B | 45373 OZ



C | 45372 OZ

CASILDA™

	ITEM #	FINISH	INCAND. BULB	W	H	EXT.	HCWO	NOTES
A	45371	OZ	(2) 100W (M)	14.75	11	7.5	7	Ⓧ (23-30W CFL)
B	45373	OZ	(4) 100W (M)	33	11	7.5	6.75	Ⓧ (23-30W CFL)
C	45372	OZ	(3) 100W (M)	23.75	11	7.5	6.75	Ⓧ (23-30W CFL)

Measurements shown in inches. U.S. & Canada Patent Pending.

CASILDA™

STERLING GOLD FINISH WITH OPTICAL CRYSTAL ACCENTS AND SATIN ETCHED CASED OPAL GLASS

MATCHING COLLECTION

See entire Casilda™ Collection on pages 256-261.



B | 45372 SGD
Wall Sconce
NOT TO SCALE



A | 45371 SGD



C | 45373 SGD

CASILDA™

	ITEM #	FINISH	INCAND. BULB	W	H	EXT.	HCWO	NOTES
A	45371	SGD	(2) 100W (M)	14.75	11	7.5	7	Ⓧ (23-30W CFL)
B	45372	SGD	(3) 100W (M)	23.75	11	7.5	6.75	Ⓧ (23-30W CFL)
C	45373	SGD	(4) 100W (M)	33	11	7.5	6.75	Ⓧ (23-30W CFL)

Measurements shown in inches. U.S. & Canada Patent Pending.

LACEY™

ANTIQUPE PEWTER OR MISSION BRONZE™
FINISH WITH SATIN ETCHED WHITE GLASS &
WHITE TRANSLUCENT ORGANZA OUTER SHADES



A | 45281 AP
Wall Sconce
NOT TO SCALE



B | 45282 AP



C | 45283 AP

MATCHING COLLECTION

See entire Lacey™
Collection on
pages 270-275.



D | 45284 AP



E | 45282 MIZ
Wall Sconce
NOT TO SCALE



F | 45283 MIZ



G | 45284 MIZ

LACEY™

	ITEM #	FINISH	INCAND. BULB	W	H	EXT.	HCWO	NOTES
A	45281	AP	(1) 60W (C)	5	10.75	7	6.5	Ⓚ
B	45282	AP	(2) 60W (C)	14	10	8.25	6.75	Ⓚ
C	45283	AP	(3) 60W (C)	22	10	8.25	7	Ⓚ
D	45284	AP	(4) 60W (C)	31	10	8.25	7	Ⓚ
E	45282	MIZ	(2) 60W (C)	14	10	8.25	6.75	Ⓚ
F	45283	MIZ	(3) 60W (C)	22	10	8.25	7	Ⓚ
G	45284	MIZ	(4) 60W (C)	31	10	8.25	7	Ⓚ

Measurements shown in inches. U.S. & Canada Patent Pending.



Stelata™ 3 Light Bath 45629 PN & 2 Light Bath 45628 PN | Page 449

STELATA™

POLISHED NICKEL & SATIN NICKEL FINISH WITH SATIN ETCHED CASED OPAL GLASS



A | 45628 PN



B | 45629 PN



C | 45630 PN



D | 45627 PN
Wall Sconce
NOT TO SCALE

STELATA™

	ITEM #	FINISH	INCAND. BULB	W	H	EXT.	HCWO	NOTES
A	45628	PN	(2) 100W (M)	12.5	7	5	4.5	ⓓ (23-30W CFL)
B	45629	PN	(3) 100W (M)	20.75	7	5.25	4.5	ⓓ (23-30W CFL)
C	45630	PN	(4) 100W (M)	29.25	7	5	4.5	ⓓ (23-30W CFL)
D	45627	PN	(1) 100W (M)	5	12	6	6	ⓓ (23-30W CFL)

Measurements shown in inches. U.S. & Canada Patent Pending.

MARANA™

POLISHED CHROME FINISH WITH
SATIN ETCHED CASED OPAL GLASS



A | 45611 CH
Wall Sconce
NOT TO SCALE



B | 45612 CH



C | 45613 CH



D | 45614 CH

MARANA™

	ITEM #	FINISH	INCAND. BULB	W	H	EXT.	HCWO	NOTES
A	45611	CH	(1) 100W (M)	6	8.5	8	6.5	Ⓧ (23-30W CFL) May be installed on wall with glass up or down.
B	45612	CH	(2) 100W (M)	16	8.75	8	2.25	Ⓧ (23-30W CFL) May be installed on wall with glass up or down.
C	45613	CH	(3) 100W (M)	24	8.75	8	2.25	Ⓧ (23-30W CFL) May be installed on wall with glass up or down.
D	45614	CH	(4) 100W (M)	36	8.75	8	2.25	Ⓧ (23-30W CFL) May be installed on wall with glass up or down.

Measurements shown in inches. U.S. & Canada Patent Pending.

MARANA™

OIL RUBBED BRONZE FINISH WITH SATIN ETCHED CASED OPAL GLASS



A | 45612 ORZ



B | 45613 ORZ



D | 45611 ORZ
Wall Sconce
NOT TO SCALE



C | 45614 ORZ

MARANA™

ITEM #	FINISH	INCAND. BULB	W	H	EXT.	HCWO	NOTES
A	ORZ	(2) 100W (M)	16	8.75	8	2.25	Ⓧ (23-30W CFL) May be installed on wall with glass up or down.
B	ORZ	(3) 100W (M)	24	8.75	8	2.25	Ⓧ (23-30W CFL) May be installed on wall with glass up or down.
C	ORZ	(4) 100W (M)	36	8.75	8	2.25	Ⓧ (23-30W CFL) May be installed on wall with glass up or down.
D	ORZ	(1) 100W (M)	6	8.5	8	6.5	Ⓧ (23-30W CFL) May be installed on wall with glass up or down.

Measurements shown in inches. U.S. & Canada Patent Pending.

SELENE™

POLISHED CHROME FINISH WITH
SATIN ETCHED CASED OPAL GLASS



A | 45431 CH
Wall Sconce
NOT TO SCALE



B | 45432 CH



C | 45433 CH



D | 45434 CH

SELENE™

	ITEM #	FINISH	INCAND. BULB	W	H	EXT.	HCWO	NOTES
A	45431	CH	(1) 100W (M)	7.5	9.25	5.5	4.25	Ⓧ (23-30W CFL)
B	45432	CH	(2) 50W (G9) Ⓧ	16	5.25	5.25	2.25	Ⓧ Halogen light source.
C	45433	CH	(3) 50W (G9) Ⓧ	24	5.25	5.25	2.25	Ⓧ Halogen light source.
D	45434	CH	(4) 50W (G9) Ⓧ	32.25	5.25	5.25	2.25	Ⓧ Halogen light source.

Measurements shown in inches. U.S. & Canada Patent Pending.

COMO™

POLISHED CHROME FINISH WITH
INNER ETCHED GLASS SHADES &
CLEAR OUTER GLASS PANEL



A | 45171 CH



B | 45172 CH



C | 45173 CH

COMO™

ITEM #	FINISH	INCAND. BULB	W	H	EXT.	HCWO	NOTES	
A	45171	CH	(2) 50W (G9)	15.75	5.5	4.5	2.5	Halogen light source. May be installed on wall with glass up or down.
B	45172	CH	(3) 50W (G9)	21.75	5.5	4.5	2.5	Halogen light source. May be installed on wall with glass up or down.
C	45173	CH	(4) 50W (G9)	27.75	5.5	4.5	2.5	Halogen light source. May be installed on wall with glass up or down.

Measurements shown in inches. U.S. & Canada Patent Pending.

TULLY™

ANTIQUE PEWTER FINISH WITH
SATIN ETCHED CASED OPAL GLASS



A | 45149 AP
Wall Sconce
NOT TO SCALE



B | 45150 AP



C | 45151 AP



D | 45152 AP



E | 45193 AP

TULLY™

ITEM #	FINISH	INCAND. BULB	W	H	EXT.	HCWO	NOTES	
A	45149	AP	(1) 100W (M)	5	6.5	6.75	4	Ⓧ (18-25W CFL) May be installed on wall with glass up or down.
B	45150	AP	(2) 100W (M)	15	6.5	6.75	4	Ⓧ (18-25W CFL) May be installed on wall with glass up or down.
C	45151	AP	(3) 100W (M)	24	6.5	6.75	4	Ⓧ (18-25W CFL) May be installed on wall with glass up or down.
D	45152	AP	(4) 100W (M)	32	6.5	6.75	4	Ⓧ (18-25W CFL) May be installed on wall with glass up or down.
E	45193	AP	(5) 100W (M)	40.25	6.5	6.75	4	Ⓧ (18-25W CFL) May be installed on wall with glass up or down.

Measurements shown in inches. U.S. & Canada Patent Pending.

TULLY™

POLISHED CHROME FINISH WITH
SATIN ETCHED CASED OPAL GLASS



A | 45150 CH



B | 45151 CH



C | 45152 CH



D | 45193 CH



E | 45149 CH
Wall Sconce
NOT TO SCALE

TULLY™

	ITEM #	FINISH	INCAND. BULB	W	H	EXT.	NOTES
A	45150	CH	(2) 100W (M)	15	6.5	6.75	Ⓧ (18-25W CFL) May be installed on wall with glass up or down.
B	45151	CH	(3) 100W (M)	24	6.5	6.75	Ⓧ (18-25W CFL) May be installed on wall with glass up or down.
C	45152	CH	(4) 100W (M)	32	6.5	6.75	Ⓧ (18-25W CFL) May be installed on wall with glass up or down.
D	45193	CH	(5) 100W (M)	40.25	6.5	6.75	Ⓧ (18-25W CFL) May be installed on wall with glass up or down.
E	45149	CH	(1) 100W (M)	5	6.5	6.75	Ⓧ (18-25W CFL) May be installed on wall with glass up or down.

Measurements shown in inches. U.S. & Canada Patent Pending.

BAZELY™

POLISHED CHROME FINISH &
CLEAR RIBBED GLASS WITH INSIDE ETCH



A | 45477 CH
Wall Sconce
NOT TO SCALE



B | 45478 CH



C | 45479 CH



D | 45480 CH

BAZELY™

	ITEM #	FINISH	INCAND. BULB	W	H	EXT.	HCWO	NOTES
A	45477	CH	(1) 50W (G9)	6	5	4.5	2.75	Halogen light source. May be installed on wall with glass up and down.
B	45478	CH	(2) 50W (G9)	15	5	4.5	2.75	Halogen light source. May be installed on wall with glass up and down.
C	45479	CH	(3) 50W (G9)	24	5	4.5	2.75	Halogen light source. May be installed on wall with glass up and down.
D	45480	CH	(4) 50W (G9)	33	5	4.5	2.75	Halogen light source. May be installed on wall with glass up and down.

Measurements shown in inches. U.S. & Canada Patent Pending.

BAZELY™

BRUSHED NICKEL FINISH WITH
CLEAR RIBBED GLASS WITH INSIDE ETCH



A | 45478 NI



B | 45479 NI



C | 45480 NI

BAZELY™

	ITEM #	FINISH	INCAND. BULB	W	H	EXT.	HCWO	NOTES
A	45478	NI	(2) 50W (G9)	15	5	4.5	2.75	Halogen light source. May be installed on wall with glass up or down.
B	45479	NI	(3) 50W (G9)	24	5	4.5	2.75	Halogen light source. May be installed on wall with glass up or down.
C	45480	NI	(4) 50W (G9)	33	5	4.5	2.75	Halogen light source. May be installed on wall with glass up or down.

Measurements shown in inches. U.S. & Canada Patent Pending.

O'HARA

POLISHED CHROME FINISH WITH
SATIN ETCHED CASED OPAL GLASS



A | 45500 CH
Wall Sconce
NOT TO SCALE



B | 45501 CH



C | 45502 CH



D | 45503 CH

O'HARA

ITEM #	FINISH	INCAND. BULB	W	H	EXT.	HCWO	NOTES	
A	45500	CH	(1) 50W (G9)	5	6.5	5.25	4	Halogen light source. May be installed on wall with glass up or down.
B	45501	CH	(2) 50W (G9)	13	6.25	5	4	Halogen light source. May be installed on wall with glass up or down.
C	45502	CH	(3) 50W (G9)	22	6.25	5	4	Halogen light source. May be installed on wall with glass up or down.
D	45503	CH	(4) 50W (G9)	31	6.25	5	4	Halogen light source. May be installed on wall with glass up or down.

Measurements shown in inches. U.S. & Canada Patent Pending.

METRO PARK™

BRUSHED NICKEL FINISH WITH
SATIN ETCHED CASED OPAL GLASS



A | 45138 NI



B | 45139 NI



C | 45140 NI

MATCHING MIRROR

41011 NI
See page 413 or
kichler.com.



METRO PARK™

	ITEM #	FINISH	INCAND. BULB	W	H	EXT.	HCWO	NOTES
A	45138	NI	(2) 60W (C)	12.75	6.5	5.25	4.25	Ⓧ G Type lamp recommended.
B	45139	NI	(3) 60W (C)	21.75	6.75	5.5	4.25	Ⓧ G Type lamp recommended.
C	45140	NI	(4) 60W (C)	30.75	6.5	5.5	4.25	Ⓧ G Type lamp recommended.

Measurements shown in inches. U.S. & Canada Patent Pending.

TUBES™

BRUSHED NICKEL FINISH WITH
SATIN ETCHED CASED OPAL GLASS



A | 5966 NI
NOT TO SCALE

MATCHING MIRROR

41011 NI
See page 413 or
kichler.com.



B | 5967 NI



C | 5968 NI

TUBES™

	ITEM #	FINISH	INCAND. BULB	W	H	EXT.	HCWO	NOTES
A	5966	NI	(2) 50W (G9)	13.75	4.75	5.25	2.25	Halogen light source.
B	5967	NI	(3) 50W (G9)	20.75	4.75	5.25	2.25	Halogen light source.
C	5968	NI	(4) 50W (G9)	28	4.75	5.25	2.25	Halogen light source.

Measurements shown in inches. U.S. & Canada Patent Pending.

KEO™

POLISHED CHROME FINISH WITH
SATIN ETCHED CASÉD OPAL GLASS



A | 45601 CH
Wall Sconce
NOT TO SCALE



B | 45602 CH



C | 45603 CH

KEO™

ITEM #	FINISH	INCAND. BULB	W	H	EXT.	HCWO	NOTES	
A	45601	CH	(1) 50W (G9) Ⓛ	7	6	5	3	Ⓛ May be installed on wall with glass up or down.
B	45602	CH	(2) 50W (G9) Ⓛ	16.75	5.5	5	2.75	Ⓛ May be installed on wall with glass up or down.
C	45603	CH	(3) 50W (G9) Ⓛ	28	5.5	5	2.75	Ⓛ May be installed on wall with glass up or down.

Measurements shown in inches.

SUSPENSION™

BRUSHED NICKEL FINISH WITH
SATIN ETCHED CASED OPAL GLASS

MATCHING COLLECTION

See entire Suspension™
Collection on
pages 88-89.



A | 45316 NI



B | 45317 NI



C | 45319 NI

SUSPENSION™

	ITEM #	FINISH	INCAND. BULB	W	H	EXT.	HCWO	NOTES
A	45316	NI	(2) 60W (C/K)	20	5	5	2.5	Krypton bulb included.
B	45317	NI	(3) 60W (C/K)	30.25	5	5	2.5	Krypton bulb included.
C	45319	NI	(5) 60W (C/K)	50.75	5	5	2.5	Krypton bulb included.

Measurements shown in inches. U.S. & Canada Patent Pending.

SUSPENSION™

POLISHED CHROME FINISH WITH
SATIN ETCHED CASED OPAL GLASS



A | 45316 CH









B | 45317 CH



C | 45319 CH

SUSPENSION™

	ITEM #	FINISH	INCAND. BULB	W	H	EXT.	HCWO	NOTES
A	45316	CH	(2) 60W (C/K) 	20	5	5	2.5	 Krypton bulb included.
B	45317	CH	(3) 60W (C/K) 	30.25	5	5	2.5	 Krypton bulb included.
C	45319	CH	(5) 60W (C/K) 	50.75	5	5	2.5	 Krypton bulb included.

Measurements shown in inches. U.S. & Canada Patent Pending.

STRUCTURES™

BRUSHED NICKEL FINISH WITH SATIN ETCHED
GLASS OR OLDE BRONZE® FINISH WITH
LIGHT UMBER ETCHED GLASS



A | 6963 NI
Wall Sconce
NOT TO SCALE



B | 6162 NI, OZ



C | 6463 NI, OZ



D | 6464 NI, OZ

STRUCTURES™

ITEM #	FINISH	INCAND. BULB	W	H	EXT.	HCWO	NOTES
A	6963 NI	(1) 100W (MNCN)	9	7.5	10.5	2.5	Halogen light source.
B	6162 NI, OZ	(2) 100W (MNCN)	21	7.5	10.5	2.5	Halogen light source.
C	6463 NI, OZ	(3) 100W (MNCN)	30	8.75	10.5	2.5	Halogen light source.
D	6464 NI, OZ	(4) 100W (MNCN)	40	8.5	10.5	2.25	Halogen light source.

Measurements shown in inches. U.S. Patent No. D512,177: A, B, C, D. U.S. Patent No. D511,858: C. U.S. Patent No. D576,761, D511,858: D.

STRUCTURES™

POLISHED CHROME FINISH
WITH SATIN ETCHED GLASS



A | 6162 CH



B | 6463 CH



C | 6464 CH

MATCHING MIRROR

41056 NI
See page 413 or
kichler.com.



MATCHING COLLECTION

See entire Structures™
Collection on
pages 90-91.



STRUCTURES™

	ITEM #	FINISH	INCAND. BULB	W	H	EXT.	HCWO	NOTES
A	6162	CH	(2) 100W (MNCN)	21	7.5	10.5	2.5	Halogen light source.
B	6463	CH	(3) 100W (MNCN)	30	8.75	10.5	2.5	Halogen light source.
C	6464	CH	(4) 100W (MNCN)	40	8.5	10.5	2.25	Halogen light source.

Measurements shown in inches. U.S. Patent No. D512,177; A. U.S. Patent Design No. D511,858; D510,452; B. U.S. Patent Design No. D511,858; D576,761; C.





Caparros™ 3 Light Bath 45133 NI & Mini Pendant 42434 NI | Page 467

CAPARROS™

BRUSHED NICKEL FINISH WITH
CLEAR RIBBED GLASS



Shown as
Mini Pendant - 7.75" H.

CONVERTIBLE

Create two distinct lighting
options with one fixture:
Mini Pendant or Semi Flush.

A | 42434 NI



Shown as
Semi Flush - 8.5" H.



B | 45132 NI



C | 45133 NI



D | 45134 NI

CAPARROS™

ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/STEM	EXT.	HCWO	NOTES	
A	42434	NI	(1) 100W (M) A19 / 60W S21	6	7.75	46	68	36	---	---	Ⓜ (23-30W CFL) Add. chain 2996 NI, add. stem 2999 (12") NI and/or 2997 NI (24") NI. Sloped ceiling kit included.
B	45132	NI	(2) 100W (M) A19 / 60W S21	17.5	10.25	---	---	---	8.5	4.25	Ⓜ (23-30W CFL)
C	45133	NI	(3) 100W (M) A19 / 60W S21	24	10.25	---	---	---	8.5	4.25	Ⓜ (23-30W CFL)
D	45134	NI	(4) 100W (M) A19 / 60W S21	32.25	10.25	---	---	---	8.5	4.25	Ⓜ (23-30W CFL)

Measurements shown in inches. U.S. & Canada Patent Pending.

GRANBY™

BRUSHED PEWTER, OLDE BRONZE®
OR POLISHED CHROME FINISH WITH
SATIN ETCHED CASED OPAL GLASS



A | 45358 CH
Wall Sconce
NOT TO SCALE



B | 45359 CH



C | 45360 CH

MATCHING MIRROR

41011 CH, NBR, NI, OZ
See page 413 or
kichler.com.



MATCHING COLLECTION

See entire Granby™
Collection on
pages 290-291.



D | 45361 CH

GRANBY™

ITEM #	FINISH	INCAND. BULB	W	H	EXT.	HCWO	NOTES	
A	45358	BPT, CH, OZ	(1) 100W (M)	5.75	14	7.5	7	Ⓟ (18-25W CFL) May be installed on wall with glass up or down.
B	45359	BPT, CH, OZ	(2) 100W (M)	17	9.5	6.5	6.5	Ⓟ (18-25W CFL) May be installed on wall with glass up or down.
C	45360	BPT, CH, OZ	(3) 100W (M)	25	9.5	6.5	6.5	Ⓟ (18-25W CFL) May be installed on wall with glass up or down.
D	45361	BPT, CH, OZ	(4) 100W (M)	32.75	9.5	6.75	6.5	Ⓟ (18-25W CFL) May be installed on wall with glass up or down.

Measurements shown in inches. U.S. & Canada Patent Pending.



A | 45358 BPT
Wall Sconce
NOT TO SCALE



B | 45359 BPT



C | 45360 BPT



D | 45361 BPT



A | 45358 OZ
Wall Sconce
NOT TO SCALE



B | 45359 OZ



C | 45360 OZ



D | 45361 OZ

BELLAMY™

ANTIQUE PEWTER FINISH WITH
SATIN ETCHED CASED OPAL GLASS



A | 45161 AP
Wall Sconce
NOT TO SCALE



B | 45162 AP



C | 45163 AP



D | 45164 AP



E | 42164 AP
Directional Rail Light

BELLAMY™

ITEM #	FINISH	INCAND. BULB	W	H	L	EXT.	HCWO	NOTES
A	AP	(1) 60W (C/K)	6	13	---	8.75	6.25	Krypton bulb included. May be installed on wall with glass up or down.
B	AP	(2) 60W (C/K)	15	7	---	7.25	4.25	Krypton bulb included. May be installed on wall with glass up or down.
C	AP	(3) 60W (C/K)	23.75	7	---	7.25	4.25	Krypton bulb included. May be installed on wall with glass up or down.
D	AP	(4) 60W (C/K)	33	7	---	7.25	3.75	Krypton bulb included. May be installed on wall with glass up or down.
E	AP	(4) 50W (GU10)	5.5	8.75	34.25	7.5	2.75	Halogen light source. May be installed on wall with glass up or down.

Measurements shown in inches.

BELLAMY™

OLDE BRONZE® FINISH WITH
UMBER ETCHED GLASS



A | 45162 OZ



B | 45163 OZ



C | 45164 OZ



E | 45161 OZ
Wall Sconce
NOT TO SCALE



D | 42164 OZ
Directional Rail Light

BELLAMY™

ITEM #	FINISH	INCAND. BULB	W	H	L	EXT.	HCWO	NOTES
A	OZ	(2) 60W (C/K) Ⓛ	15	7	---	7.25	4.25	Ⓛ Krypton bulb included. May be installed on wall with glass up or down.
B	OZ	(3) 60W (C/K) Ⓛ	23.75	7	---	7.25	4.25	Ⓛ Krypton bulb included. May be installed on wall with glass up or down.
C	OZ	(4) 60W (C/K) Ⓛ	33	7	---	7.25	3.75	Ⓛ Krypton bulb included. May be installed on wall with glass up or down.
D	OZ	(4) 50W (GU10) Ⓛ	5.5	8.75	34.25	7.5	2.75	Ⓛ Krypton bulb included. May be installed on wall with glass up or down.
E	OZ	(1) 60W (C/K) Ⓛ	6	13	---	8.75	6.25	Ⓛ Halogen light source. May be installed on wall with glass up or down.

Measurements shown in inches.

POCELONA™

POLISHED CHROME FINISH WITH WHITE
PORCELAIN DETAILS & CASED OPAL GLASS



A | 5367 CH
Wall Sconce
NOT TO SCALE



B | 5368 CH



C | 5369 CH



D | 5370 CH

MATCHING MIRROR

41067 CH

See page 413 or
kichler.com.



POCELONA™

ITEM #	FINISH	INCAND. BULB	W	H	EXT.	HCWO	NOTES	
A	5367	CH	(1) 100W (M)	5.5	9	7.5	5.25	Ⓧ May be installed on wall with glass up or down.
B	5368	CH	(2) 100W (M)	14.5	9	6.25	6.5	Ⓧ May be installed on wall with glass up or down.
C	5369	CH	(3) 100W (M)	24	9	7.5	2.25	Ⓧ May be installed on wall with glass up or down.
D	5370	CH	(4) 100W (M)	33	9	7.5	2.25	Ⓧ May be installed on wall with glass up or down.

Measurements shown in inches.

CORA

POLISHED CHROME FINISH WITH
INSIDE ETCHED CLEAR RIBBED GLASS



A | 45642 CH



B | 45643 CH



D | 45641 CH
Wall Sconce
NOT TO SCALE



C | 45644 CH

CORA

ITEM #	FINISH	INCAND. BULB	W	H	EXT.	HCWO	NOTES	
A	45642	CH	(2) 100W (M)	16	9.5	7.5	5.25	Ⓢ (18-25W CFL) May be installed on wall with glass up or down.
B	45643	CH	(3) 100W (M)	24	9.5	7.5	5.25	Ⓢ (18-25W CFL) May be installed on wall with glass up or down.
C	45644	CH	(4) 100W (M)	32.5	9.5	7.5	5.25	Ⓢ (18-25W CFL) May be installed on wall with glass up or down.
D	45641	CH	(1) 100W (M)	5	9.5	7	5.25	Ⓢ (18-25W CFL) May be installed on wall with glass up or down.

Measurements shown in inches. U.S. & Canada Patent Pending.

WHARTON™

BRUSHED NICKEL FINISH WITH
SATIN ETCHED CASED OPAL GLASS



A | 5359 NI
Wall Sconce
NOT TO SCALE



B | 5360 NI



C | 5361 NI



D | 5362 NI

WHARTON™

ITEM #	FINISH	INCAND. BULB	W	H	EXT.	HCWO	NOTES	
A	5359	NI	(1) 100W (M)	4.75	9	6	4.5	Ⓧ (9-13W CFL) May be installed on wall with glass up or down.
B	5360	NI	(2) 100W (M)	13.75	9	6	2.25	Ⓧ (9-13W CFL) May be installed on wall with glass up or down.
C	5361	NI	(3) 100W (M)	21.75	9	6	6.75	Ⓧ (9-13W CFL) May be installed on wall with glass up or down.
D	5362	NI	(4) 100W (M)	30.25	9	6	6.75	Ⓧ (9-13W CFL) May be installed on wall with glass up or down.

Measurements shown in inches. U.S. & Canada Patent Pending.

UPTOWN

BRUSHED NICKEL FINISH WITH
SATIN ETCHED CASED OPAL GLASS



A | 5402 NI
Not To Scale

MATCHING MIRROR

41011 NI
See page 413 or
kichler.com.



B | 5403 NI



C | 5404 NI

UPTOWN

	ITEM #	FINISH	INCAND. BULB	W	H	EXT.	HCWO	NOTES
A	5402	NI	(2) 100W (M)	15.25	7.5	6.5	3.75	Ⓧ May be installed on wall with glass up or down.
B	5403	NI	(3) 100W (M)	24	7.5	6.5	3.75	Ⓧ May be installed on wall with glass up or down.
C	5404	NI	(4) 100W (M)	32.75	7.5	6.5	3.75	Ⓧ May be installed on wall with glass up or down.

Measurements shown in inches.

LEGÉ™

BRUSHED NICKEL FINISH WITH
OPAL ETCHED GLASS



A | 5051 NI
Wall Sconce
NOT TO SCALE



B | 5052 NI



C | 5053 NI



D | 5054 NI

MATCHING MIRROR

41011 NI
See page 413 or
kichler.com.



LEGÉ™

ITEM #	FINISH	INCAND. BULB	W	H	EXT.	HCWO	NOTES
A	5051	NI (1) 100W (M)	4.75	8	5	3.75	Ⓧ (23-30W CFL) May be installed on wall with glass up or down.
B	5052	NI (2) 100W (M)	15.25	9	5.5	6.75	Ⓧ (23-30W CFL) May be installed on wall with glass up or down.
C	5053	NI (3) 100W (M)	22.75	9	5.5	2.25	Ⓧ (23-30W CFL) May be installed on wall with glass up or down.
D	5054	NI (4) 100W (M)	30.5	9	5.5	2.25	Ⓧ (23-30W CFL) May be installed on wall with glass up or down.

Measurements shown in inches.

CYLINDERS

POLISHED NICKEL FINISH WITH
SATIN ETCHED CASED OPAL GLASS



A | 5437 PN



B | 5438 PN



D | 5436 PN
Wall Sconce
NOT TO SCALE



C | 5439 PN

CYLINDERS

	ITEM #	FINISH	INCAND. BULB	W	H	EXT.	HCWO	NOTES
A	5437	PN	(2) 100W (M)	12.75	8	5.75	2.5	ⓓ May be installed on wall with glass up or down.
B	5438	PN	(3) 100W (M)	20.5	8	5.75	5.75	ⓓ May be installed on wall with glass up or down.
C	5439	PN	(4) 100W (M)	28.5	8	5.75	5.75	ⓓ May be installed on wall with glass up or down.
D	5436	PN	(1) 100W (M)	4.75	8	5.75	5.75	ⓓ May be installed on wall with glass up or down.

Measurements shown in inches.

WELLINGTON SQUARE

CLASSIC PEWTER FINISH WITH
SATIN ETCHED WHITE GLASS



A | 45402 CLP



B | 45403 CLP



C | 45404 CLP

WELLINGTON SQUARE

	ITEM #	FINISH	INCAND. BULB	W	H	EXT.	HCWO	NOTES
A	45402	CLP	(2) 100W (M)	16	7.75	8	4.75	Ⓛ (23-30W CFL) May be installed on wall with glass up or down.
B	45403	CLP	(3) 100W (M)	24	7.75	8	4.75	Ⓛ (23-30W CFL) May be installed on wall with glass up or down.
C	45404	CLP	(4) 100W (M)	33	7.75	8	4.75	Ⓛ (23-30W CFL) May be installed on wall with glass up or down.

Measurements shown in inches. U.S. & Canada Patent Pending.

WELLINGTON SQUARE

OLDE BRONZE® FINISH WITH SATIN ETCHED WHITE GLASS



C | 45402 OZ



A | 45403 OZ



B | 45404 OZ

MATCHING MIRROR

41011 OZ
See page 413 or
kichler.com.



WELLINGTON SQUARE

	ITEM #	FINISH	INCAND. BULB	W	H	EXT.	HCWO	NOTES
A	45403	OZ	(3) 100W (M)	24	7.75	8	4.75	Ⓧ (23-30W CFL) May be installed on wall with glass up or down.
B	45404	OZ	(4) 100W (M)	33	7.75	8	4.75	Ⓧ (23-30W CFL) May be installed on wall with glass up or down.
C	45402	OZ	(2) 100W (M)	16	7.75	8	4.75	Ⓧ (23-30W CFL) May be installed on wall with glass up or down.

Measurements shown in inches. U.S. & Canada Patent Pending.

CURRITUCK™

POLISHED CHROME FINISH WITH
SATIN ETCHED CASSED OPAL GLASS



A | 45486 CH
Wall Sconce
NOT TO SCALE



B | 45487 CH



C | 45488 CH



D | 45489 CH

CURRITUCK™

ITEM #	FINISH	INCAND. BULB	W	H	EXT.	HCWO	NOTES
A	CH	(1) 100W (M)	5.25	9.75	6.5	2.5	Ⓛ (23-30W CFL) May be installed on wall with glass up or down.
B	CH	(2) 100W (M)	16	9.75	6.25	2.5	Ⓛ (23-30W CFL) May be installed on wall with glass up or down.
C	CH	(3) 100W (M)	23.25	9.75	6.25	7.5	Ⓛ (23-30W CFL) May be installed on wall with glass up or down.
D	CH	(4) 100W (M)	32.25	9.75	6.5	2.25	Ⓛ (23-30W CFL) May be installed on wall with glass up or down.

Measurements shown in inches. U.S. & Canada Patent Pending.

CURRITUCK™

OIL RUBBED BRONZE FINISH WITH SATIN ETCHED CASED OPAL GLASS



A | 45487 ORZ



B | 45488 ORZ



D | 45486 ORZ
Wall Sconce
NOT TO SCALE



C | 45489 ORZ

CURRITUCK™

ITEM #	FINISH	INCAND. BULB	W	H	EXT.	HCWO	NOTES
A	ORZ	(2) 100W (M)	16	9.75	6.25	2.5	ⓓ (23-30W CFL) May be installed on wall with glass up or down.
B	ORZ	(3) 100W (M)	23.25	9.75	6.25	2.5	ⓓ (23-30W CFL) May be installed on wall with glass up or down.
C	ORZ	(4) 100W (M)	32.25	9.75	6.5	2.5	ⓓ (23-30W CFL) May be installed on wall with glass up or down.
D	ORZ	(1) 100W (M)	5.25	9.75	6.5	2.5	ⓓ (23-30W CFL) May be installed on wall with glass up or down.

Measurements shown in inches. U.S. & Canada Patent Pending.

CAMERENA™

OLDE BRONZE® FINISH WITH
WHITE SCAVO GLASS & LIGHT UMBER INSIDE TINT



A | 45421 OZ
Wall Sconce
NOT TO SCALE



B | 45422 OZ



C | 45423 OZ



D | 45424 OZ

MATCHING COLLECTION

See entire Camerena™
Collection on
pages 286-287.



CAMERENA™

	ITEM #	FINISH	INCAND. BULB	W	H	EXT.	HCWO	NOTES
A	45421	OZ	(1) 100W (M)	6	12.5	8.75	8.5	ⓓ (23-30W CFL) May be installed on wall with glass up or down.
B	45422	OZ	(2) 100W (M)	18	9	8.25	5	ⓓ (23-30W CFL) May be installed on wall with glass up or down.
C	45423	OZ	(3) 100W (M)	24	9	8.25	5	ⓓ (23-30W CFL) May be installed on wall with glass up or down.
D	45424	OZ	(4) 100W (M)	36	9	8.25	5	ⓓ (23-30W CFL) May be installed on wall with glass up or down.

Measurements shown in inches.

CAMERENA™

BRUSHED NICKEL FINISH WITH
WHITE SCAVO GLASS



A | 45422 NI



B | 45423 NI



C | 45424 NI



D | 45421 NI
Wall Sconce
NOT TO SCALE

MATCHING COLLECTION

See entire Camerena™
Collection on
pages 286-287.



CAMERENA™

	ITEM #	FINISH	INCAND. BULB	W	H	EXT.	HCWO	NOTES
A	45422	NI	(2) 100W (M)	18	9	8.25	5	Ⓧ (23-30W CFL) May be installed on wall with glass up or down.
B	45423	NI	(3) 100W (M)	24	9	8.25	5	Ⓧ (23-30W CFL) May be installed on wall with glass up or down.
C	45424	NI	(4) 100W (M)	36	9	8.25	5	Ⓧ (23-30W CFL) May be installed on wall with glass up or down.
D	45421	NI	(1) 100W (M)	6	12.5	8.75	8.5	Ⓧ (23-30W CFL) May be installed on wall with glass up or down.

Measurements shown in inches.



Monroe™ Wall Sconce 43170 OZ | Page 485 & Chandelier 43155 OZ | Page 283

MONROE™

OLDE BRONZE® FINISH WITH
LIGHT UMBER ETCHED GLASS



A | 45054 OZ



B | 45055 OZ



C | 45056 OZ



D | 43170 OZ
Wall Sconce
NOT TO SCALE

MATCHING COLLECTION

See entire Monroe™
Collection on
pages 278-285.



MONROE™

ITEM #	FINISH	INCAND. BULB	W	H	EXT.	HCWO	NOTES	
A	45054	OZ	(2) 100W (M)	18	11.75	8	5	Ⓧ (23-30W CFL) May be installed on wall with glass up or down.
B	45055	OZ	(3) 100W (M)	24	11.5	8	5	Ⓧ (23-30W CFL) May be installed on wall with glass up or down.
C	45056	OZ	(4) 100W (M)	36	11.5	8	5	Ⓧ (23-30W CFL) May be installed on wall with glass up or down.
D	43170	OZ	(1) 100W (M)	6	14	9.25	8	Ⓧ (23-30W CFL) May be installed on wall with glass up or down.

Measurements shown in inches.

MONROE™

BRUSHED NICKEL FINISH
WITH SATIN ETCHED GLASS



A | 43170 NI
Wall Sconce
NOT TO SCALE



B | 45054 NI



C | 45055 NI



D | 45056 NI

MATCHING COLLECTION

See entire Monroe™
Collection on
pages 278-285.



MONROE™

	ITEM #	FINISH	INCAND. BULB	W	H	EXT.	HCWO	NOTES
A	43170	NI	(1) 100W (M)	6	14	9.25	8	Ⓧ (23-30W CFL) May be installed on wall with glass up or down.
B	45054	NI	(2) 100W (M)	18	11.75	8	5	Ⓧ (23-30W CFL) May be installed on wall with glass up or down.
C	45055	NI	(3) 100W (M)	24	11.5	8	5	Ⓧ (23-30W CFL) May be installed on wall with glass up or down.
D	45056	NI	(4) 100W (M)	36	11.5	8	5	Ⓧ (23-30W CFL) May be installed on wall with glass up or down.

Measurements shown in inches.

MONROE™

STERLING GOLD™ FINISH
WITH SATIN ETCHED GLASS



A | 45054 SGD



B | 45055 SGD



C | 45056 SGD



D | 43170 SGD
Wall Sconce
NOT TO SCALE

MATCHING MIRROR

41096 SGD
See page 412 or
kichler.com.



MONROE™

ITEM #	FINISH	INCAND. BULB	W	H	EXT.	HCWO	NOTES	
A	45054	SGD	(2) 100W (M)	18	11.75	8	5	Ⓧ (23-30W CFL) May be installed on wall with glass up or down.
B	45055	SGD	(3) 100W (M)	24	11.5	8	5	Ⓧ (23-30W CFL) May be installed on wall with glass up or down.
C	45056	SGD	(4) 100W (M)	36	11.5	8	5	Ⓧ (23-30W CFL) May be installed on wall with glass up or down.
D	43170	SGD	(1) 100W (M)	6	14	9.25	8	Ⓧ (23-30W CFL) May be installed on wall with glass up or down.

Measurements shown in inches.

WILTON™

CARRÉ BRONZE® FINISH WITH
ANTIQUÉ BARLEY GLASS



A | 5988 CZ



B | 5989 CZ



C | 5990 CZ

WILTON™

ITEM #	FINISH	INCAND. BULB	W	H	EXT.	HCWO	NOTES	
A	5988	CZ	(2) 100W (M)	16	10.25	8.75	5.25	Ⓧ (23-30W CFL) May be installed on wall with glass up or down.
B	5989	CZ	(3) 100W (M)	25	10.25	8.75	4.75	Ⓧ (23-30W CFL) May be installed on wall with glass up or down.
C	5990	CZ	(4) 100W (M)	34	10.25	8.75	4.75	Ⓧ (23-30W CFL) May be installed on wall with glass up or down.

Measurements shown in inches.

DRAPES

BRUSHED NICKEL FINISH WITH
CLEAR ICE GLASS



A | 6313 NI



B | 6312 NI



C | 6314 NI

MATCHING MIRROR

41011 NI
See page 413 or
kichler.com.



DRAPES

	ITEM #	FINISH	INCAND. BULB	W	H	EXT.	HCWO	NOTES
A	6313	NI	(3) 60W (C)	26.5	6.25	7	3.75	D
B	6312	NI	(2) 60W (C)	17.5	6.25	7	3.75	D
C	6314	NI	(4) 60W (C)	35.25	6.25	7	3.75	D

Measurements shown in inches.

WILLOWMORE

TANNERY BRONZE™ FINISH WITH
DISTRESSED UMBER ETCHED GLASS



A | 5927 TZ



B | 5928 TZ



C | 5929 TZ

WILLOWMORE

	ITEM #	FINISH	INCAND. BULB	W	H	EXT.	HCWO	NOTES
A	5927	TZ	(2) 100W (M)	15.5	11	7.5	7.5	(23-30W CFL) May be installed on wall with glass up or down.
B	5928	TZ	(3) 100W (M)	23.5	11	7.5	7.5	(23-30W CFL) May be installed on wall with glass up or down.
C	5929	TZ	(4) 100W (M)	31.5	11	7.5	3.5	(23-30W CFL) May be installed on wall with glass up or down.

Measurements shown in inches.

WILLOWMORE

BRUSHED NICKEL FINISH
WITH SATIN ETCHED GLASS



A | 5928 NI



B | 5927 NI



C | 5929 NI

MATCHING MIRROR

41011 NI
See page 413 or
kichler.com.



WILLOWMORE

ITEM #	FINISH	INCAND. BULB	W	H	EXT.	HCWO	NOTES	
A	5928	NI	(3) 100W (M)	23.5	11	7.5	3.5	ⓓ (23-30W CFL) May be installed on wall with glass up or down.
B	5927	NI	(2) 100W (M)	15.5	11	7.5	3.5	ⓓ (23-30W CFL) May be installed on wall with glass up or down.
C	5929	NI	(4) 100W (M)	31.5	11	7.5	3.5	ⓓ (23-30W CFL) May be installed on wall with glass up or down.

Measurements shown in inches.

CRESCENT VIEW™

BRUSHED NICKEL FINISH WITH
SATIN ETCHED CASED OPAL GLASS

MATCHING MIRROR

41011 NI

See page 413 or
kichler.com.



A | 45218 NI



B | 45220 NI

CRESCENT VIEW™

	ITEM #	FINISH	INCAND. BULB	W	H	EXT.	HCWO	NOTES
A	45218	NI	(2) 60W (C)	18	6.25	5.75	3	Ⓧ May be installed on wall vertically or horizontally.
B	45220	NI	(3) 60W (C)	24	6.25	5.75	3	Ⓧ May be installed on wall vertically or horizontally.

Measurements shown in inches. U.S. & Canada Patent Pending.

SANTIAGO ENERGY EFFICIENT

BRUSHED NICKEL & POLISHED CHROME
FINISH WITH WHITE LINEN FABRIC SHADE



A | 10885 NI




B | 10886 NI

Matte White Acrylic
Diffuser with White
Linen Fabric
Trim Ring



C | 10439 NCH
Wall Sconce
ADA Compliant



White Linen
Fabric Shade
with Matte White
Acrylic Diffuser

D | 10438 NCH
Wall Sconce
ADA Compliant
NOT TO SCALE

SANTIAGO ENERGY EFFICIENT

	FLUOR. ITEM #	FINISH	FLUOR. BULB	W	H	EXT.	HCWO	NOTES
A	10885	NI	(2) 13W (QAD4)	13	4.25	---	---	
B	10886	NI	(3) 13W (QAD4)	17.25	4.25	---	---	
C	10439	NCH	(2) 13W (G24Q-1)	11	14.25	3.75	5.25	
D	10438	NCH	(1) 13W (G24Q-1)	5.5	14.25	3.75	5.25	

Measurements shown in inches.

EILEEN™

POLISHED CHROME FINISH WITH
SATIN ETCHED CASED OPAL GLASS



A | 5096 CH
Wall Sconce
NOT TO SCALE



B | 5097 CH



C | 5098 CH



D | 5099 CH

MATCHING MIRROR

41011 CH

See page 413 or
kichler.com.



EILEEN™

ITEM #	FINISH	INCAND. BULB	W	H	EXT.	HCWO	NOTES	
A	5096	CH	(1) 100W (M)	4.5	10.75	7	5.75	Ⓚ (18-25W CFL) May be installed on wall with glass up or down.
B	5097	CH	(2) 100W (M)	14.25	9.25	6	7	Ⓚ (18-25W CFL) May be installed on wall with glass up or down.
C	5098	CH	(3) 100W (M)	24	9.25	6	7	Ⓚ (18-25W CFL) May be installed on wall with glass up or down.
D	5099	CH	(4) 100W (M)	33.75	9.25	6	7	Ⓚ (18-25W CFL) May be installed on wall with glass up or down.

Measurements shown in inches.

MATCHING COLLECTION

See entire Eileen™ Collection on pages 102-107.



EILEEN™

BRUSHED NICKEL FINISH WITH SATIN ETCHED CASÉ OPAL GLASS



A | 5097 NI
5097 NIFL



D | 5096 NI
5096 NIFL
Wall Sconce
NOT TO SCALE



B | 5098 NI
5098 NIFL



C | 5099 NI
5099 NIFL

MATCHING MIRROR

41096 NI
See page 413 or
kichler.com.



EILEEN™

ITEM #	FLOUR. ITEM #	FINISH	INCAND. BULB	FLOUR. BULB	W	H	EXT.	HCWO	NOTES
A	5097	5097 NIFL	NI	(2) 100W (M) (2) 13W (GU24)	14.25	9.25	6	7	Ⓧ (18-25W CFL) May be installed on wall with glass up or down.
B	5098	5098 NIFL	NI	(3) 100W (M) (3) 13W (GU24)	24	9.25	6	7	Ⓧ (18-25W CFL) May be installed on wall with glass up or down.
C	5099	5099 NIFL	NI	(4) 100W (M) (4) 13W (GU24)	33.75	9.25	6	7	Ⓧ (18-25W CFL) May be installed on wall with glass up or down.
D	5096	5096 NIFL	NI	(1) 100W (M) (1) 13W (GU24)	4.5	10.75	7	5.75	Ⓧ (18-25W CFL) May be installed on wall with glass up or down.

Measurements shown in inches.

EILEEN™

OLDE BRONZE® FINISH WITH
UMBER ETCHED GLASS



A | 5096 OZ
5096 OZFL
Wall Sconce
NOT TO SCALE



C | 5097 OZ
5097 OZFL



C | 5098 OZ
5098 OZFL



D | 5099 OZ
5099 OZFL

MATCHING MIRROR

41096 OZ
See page 412 or
kichler.com.



EILEEN™

ITEM #	FLOUR. ITEM #	FINISH	INCAND. BULB	FLOUR. BULB	W	H	EXT.	HCWO	NOTES	
A	5096	5096 OZFL	OZ	(1) 100W (M)	(1) 13W (GU24)	4.5	10.75	7	5.75	(18-25W CFL) May be installed on wall with glass up or down.
B	5097	5097 OZFL	OZ	(2) 100W (M)	(2) 13W (GU24)	14.25	9.25	6	7	(18-25W CFL) May be installed on wall with glass up or down.
C	5098	5098 OZFL	OZ	(3) 100W (M)	(3) 13W (GU24)	24	9.25	6	7	(18-25W CFL) May be installed on wall with glass up or down.
D	5099	5099 OZFL	OZ	(4) 100W (M)	(4) 13W (GU24)	33.75	9.25	6	7	(18-25W CFL) May be installed on wall with glass up or down.

Measurements shown in inches.

AUBREY

OLDE BRONZE® FINISH WITH
SATIN ETCHED CASED OPAL GLASS



A | 45569 OZ



B | 45570 OZ



D | 45568 OZ
Wall Sconce
NOT TO SCALE



C | 45571 OZ

MATCHING COLLECTION

See entire Aubrey
Collection on
pages 296-297.



AUBREY

ITEM #	FINISH	INCAND. BULB	W	H	EXT.	HCWO	NOTES	
A	45569	OZ	(2) 100W (M)	13	10.75	6.5	7.5	ⓓ (23-30W CFL) May be installed on wall with glass up or down.
B	45570	OZ	(3) 100W (M)	21	11	7.25	7.5	ⓓ (23-30W CFL) May be installed on wall with glass up or down.
C	45571	OZ	(4) 100W (M)	29	10.75	6.5	7.5	ⓓ (23-30W CFL) May be installed on wall with glass up or down.
D	45568	OZ	(1) 100W (M)	5.5	10.75	7.25	5.5	ⓓ (23-30W CFL) May be installed on wall with glass up or down.

Measurements shown in inches. U.S. & Canada Patent Pending.

AUBREY

POLISHED CHROME FINISH WITH
SATIN ETCHED CASED OPAL GLASS



A | 45568 CH
Wall Sconce
NOT TO SCALE



B | 45569 CH



C | 45570 CH



D | 45571 CH

MATCHING COLLECTION

See entire Aubrey
Collection on
pages 296-297.



AUBREY

	ITEM #	FINISH	INCAND. BULB	W	H	EXT.	HCWO	NOTES
A	45568	CH	(1) 100W (M)	5.5	10.75	7.25	5.5	Ⓧ (23-30W CFL) May be installed on wall with glass up or down.
B	45569	CH	(2) 100W (M)	13	10.75	6.5	7.5	Ⓧ (23-30W CFL) May be installed on wall with glass up or down.
C	45570	CH	(3) 100W (M)	21	11	7.25	7.5	Ⓧ (23-30W CFL) May be installed on wall with glass up or down.
D	45571	CH	(4) 100W (M)	29	10.75	6.5	7.5	Ⓧ (23-30W CFL) May be installed on wall with glass up or down.

Measurements shown in inches. U.S. & Canada Patent Pending.

AUBREY

BRUSHED NICKEL FINISH WITH
SATIN ETCHED CASED OPAL GLASS



A | 45569 NI



B | 45570 NI



D | 45568 NI
Wall Sconce
NOT TO SCALE



C | 45571 NI

MATCHING COLLECTION

See entire Aubrey
Collection on
pages 296-297.



AUBREY

	ITEM #	FINISH	INCAND. BULB	W	H	EXT.	HCWO	NOTES
A	45569	NI	(2) 100W (M)	13	10.75	6.5	7.5	Ⓧ (23-30W CFL) May be installed on wall with glass up or down.
B	45570	NI	(3) 100W (M)	21	11	7.25	7.5	Ⓧ (23-30W CFL) May be installed on wall with glass up or down.
C	45571	NI	(4) 100W (M)	29	10.75	6.5	7.5	Ⓧ (23-30W CFL) May be installed on wall with glass up or down.
D	45568	NI	(1) 100W (M)	5.5	10.75	7.25	5.5	Ⓧ (23-30W CFL) May be installed on wall with glass up or down.

Measurements shown in inches. U.S. & Canada Patent Pending.

LILAH

POLISHED CHROME FINISH WITH
SATIN ETCHED WHITE GLASS



A | 45550 CH
Wall Sconce
NOT TO SCALE



B | 45551 CH



C | 45552 CH



D | 45553 CH

MATCHING MIRROR

41067 CH

See page 413 or
kichler.com.



LILAH

ITEM #	FINISH	INCAND. BULB	W	H	EXT.	HCWO	NOTES
A	CH	(1) 100W (M)	5	10	6.25	4.75	Ⓧ (23-30W CFL) May be installed on wall with glass up or down.
B	CH	(2) 100W (M)	12	10	8	7.25	Ⓧ (23-30W CFL) May be installed on wall with glass up or down.
C	CH	(3) 100W (M)	20	10	8	7.25	Ⓧ (23-30W CFL) May be installed on wall with glass up or down.
D	CH	(4) 100W (M)	28	10	8	7.25	Ⓧ (23-30W CFL) May be installed on wall with glass up or down.

Measurements shown in inches.

LILAH

ANTIQUE PEWTER FINISH WITH
SATIN ETCHED WHITE GLASS



A | 45551 AP



B | 45552 AP



C | 45553 AP



D | 45550 AP
Wall Sconce
NOT TO SCALE

MATCHING COLLECTION

See entire Lilah
Collection on
pages 304-305.



LILAH

	ITEM #	FINISH	INCAND. BULB	W	H	EXT.	HCWO	NOTES
A	45551	AP	(2) 100W (M)	12	10	8	7.25	Ⓧ (23-30W CFL) May be installed with glass up or down.
B	45552	AP	(3) 100W (M)	20	10	8	7.25	Ⓧ (23-30W CFL) May be installed with glass up or down.
C	45553	AP	(4) 100W (M)	28	10	8	7.25	Ⓧ (23-30W CFL) May be installed with glass up or down.
D	45550	AP	(1) 100W (M)	5	10	6.25	4.75	Ⓧ (23-30W CFL) May be installed with glass up or down.

Measurements shown in inches.

LILAH

OLDE BRONZE® FINISH WITH
SATIN ETCHED WHITE GLASS



A | 45550 OZ
Wall Sconce
NOT TO SCALE



B | 45551 OZ



C | 45552 OZ



D | 45553 OZ

MATCHING COLLECTION

See entire Lilah
Collection on
pages 304-305.



LILAH

	ITEM #	FINISH	INCAND. BULB	W	H	EXT.	HCWO	NOTES
A	45550	OZ	(1) 100W (M)	5	10	6.25	4.75	ⓓ (23-30W CFL) May be installed on wall with glass up or down.
B	45551	OZ	(2) 100W (M)	12	10	8	7.25	ⓓ (23-30W CFL) May be installed on wall with glass up or down.
C	45552	OZ	(3) 100W (M)	20	10	8	7.25	ⓓ (23-30W CFL) May be installed on wall with glass up or down.
D	45553	OZ	(4) 100W (M)	28	10	8	7.25	ⓓ (23-30W CFL) May be installed on wall with glass up or down.

Measurements shown in inches.

SHAILENE

OLDE BRONZE® FINISH WITH
SATIN ETCHED GLASS



A | 45573 OZ



B | 45574 OZ



C | 45575 OZ



D | 45572 OZ
Wall Sconce
NOT TO SCALE

MATCHING COLLECTION

See entire Shailene
Collection on
pages 108-109.



SHAILENE

ITEM #	FINISH	INCAND. BULB	W	H	EXT.	HCWO	NOTES
A	OZ	(2) 100W (M)	12.5	8.25	6	5.25	Ⓧ (23-30W CFL) May be installed on wall with glass up or down.
B	OZ	(3) 100W (M)	21	8.25	6	5.25	Ⓧ (23-30W CFL) May be installed on wall with glass up or down.
C	OZ	(4) 100W (M)	29.5	8.25	6	5.25	Ⓧ (23-30W CFL) May be installed on wall with glass up or down.
D	OZ	(1) 100W (M)	5	8.25	6	4.75	Ⓧ (23-30W CFL) May be installed on wall with glass up or down.

Measurements shown in inches.

SHAILENE

POLISHED CHROME FINISH WITH
SATIN ETCHED GLASS



A | 45572 CH
Wall Sconce
NOT TO SCALE



B | 45573 CH



C | 45574 CH



D | 45575 CH

MATCHING MIRROR

41067 CH
See page 413 or
kichler.com.



SHAILENE

	ITEM #	FINISH	INCAND. BULB	W	H	EXT.	HCWO	NOTES
A	45572	CH	(1) 100W (M)	5	8.25	6	4.75	Ⓢ (23-30W CFL) May be installed on wall with glass up or down.
B	45573	CH	(2) 100W (M)	12.5	8.25	6	5.25	Ⓢ (23-30W CFL) May be installed on wall with glass up or down.
C	45574	CH	(3) 100W (M)	21	8.25	6	5.25	Ⓢ (23-30W CFL) May be installed on wall with glass up or down.
D	45575	CH	(4) 100W (M)	29.5	8.25	6	5.25	Ⓢ (23-30W CFL) May be installed on wall with glass up or down.

Measurements shown in inches.

SHAILENE

BRUSHED NICKEL FINISH WITH
SATIN ETCHED GLASS



A | 45573 NI



B | 45574 NI



C | 45575 NI



D | 45572 NI
Wall Sconce
NOT TO SCALE

MATCHING COLLECTION

See entire Shailene
Collection on
pages 108-109.



SHAILENE

ITEM #	FINISH	INCAND. BULB	W	H	EXT.	HCWO	NOTES
A	NI	(2) 100W (M)	12.5	8.25	6	5.25	Ⓧ (23-30W CFL) May be installed on wall with glass up or down.
B	NI	(3) 100W (M)	21	8.25	6	5.25	Ⓧ (23-30W CFL) May be installed on wall with glass up or down.
C	NI	(4) 100W (M)	29.5	8.25	6	5.25	Ⓧ (23-30W CFL) May be installed on wall with glass up or down.
D	NI	(1) 100W (M)	5	8.25	6	4.75	Ⓧ (23-30W CFL) May be installed on wall with glass up or down.

Measurements shown in inches.

KEIRAN

BRUSHED NICKEL FINISH WITH
SATIN ETCHED WHITE GLASS



A | 45504 NI
Wall Sconce
NOT TO SCALE



B | 45512 NI



C | 45513 NI



D | 45514 NI

MATCHING COLLECTION

See entire Keiran
Collection on
pages 298-299.



KEIRAN

	ITEM #	FINISH	INCAND. BULB	W	H	EXT.	HCWO	NOTES
A	45504	NI	(1) 100W (M)	6	8.5	9.25	3.25	ⓓ (23-30W CFL) May be installed on wall with glass up or down.
B	45512	NI	(2) 100W (M)	14	8.25	8.5	4.75	ⓓ (23-30W CFL) May be installed on wall with glass up or down.
C	45513	NI	(3) 100W (M)	22	8.25	8.5	4.75	ⓓ (23-30W CFL) May be installed on wall with glass up or down.
D	45514	NI	(4) 100W (M)	30	8.25	8.5	4.75	ⓓ (23-30W CFL) May be installed on wall with glass up or down.

Measurements shown in inches. U.S. & Canada Patent Pending.

KEIRAN

OLDE BRONZE® FINISH WITH SATIN ETCHED WHITE GLASS



Rectangle Shape Arm Design

A | 45512 OZ



D | 45504 OZ
Wall Sconce
NOT TO SCALE



B | 45513 OZ



C | 45514 OZ

MATCHING COLLECTION

See entire Keiran Collection on pages 298-299.



KEIRAN

ITEM #	FINISH	INCAND. BULB	W	H	EXT.	HCWO	NOTES
A	45512 OZ	(2) 100W (M)	14	8.25	8.5	4.75	ⓓ (23-30W CFL) May be installed on wall with glass up or down.
B	45513 OZ	(3) 100W (M)	22	8.25	8.5	4.75	ⓓ (23-30W CFL) May be installed on wall with glass up or down.
C	45514 OZ	(4) 100W (M)	30	8.25	8.5	4.75	ⓓ (23-30W CFL) May be installed on wall with glass up or down.
D	45504 OZ	(1) 100W (M)	6	8.5	9.25	3.25	ⓓ (23-30W CFL) May be installed on wall with glass up or down.

Measurements shown in inches. U.S. & Canada Patent Pending.

SERINA

BLACK FINISH WITH
SATIN ETCHED WHITE GLASS



A | 45731 BK
Wall Sconce
NOT TO SCALE



B | 45732 BK



C | 45733 BK



D | 45734 BK

MATCHING COLLECTION

See entire Serina
Collection on
pages 288-289.



SERINA

	ITEM #	FINISH	INCAND. BULB	W	H	EXT.	HCWO	NOTES
A	45731	BK	(1) 100W (M)	5.5	9	6.25	5.75	Ⓧ (23-30W CFL) May be installed with glass up or down.
B	45732	BK	(2) 100W (M)	14.5	8	6.25	5.75	Ⓧ (23-30W CFL) May be installed with glass up or down.
C	45733	BK	(3) 100W (M)	22.5	8	6.25	5.5	Ⓧ (23-30W CFL) May be installed with glass up or down.
D	45734	BK	(4) 100W (M)	31	8	6.25	5.5	Ⓧ (23-30W CFL) May be installed with glass up or down.

Measurements shown in inches. U.S. & Canada Patent Pending.

SERINA

BRUSHED NICKEL FINISH WITH
SATIN ETCHED WHITE GLASS



A | 45732 NI



B | 45733 NI



D | 45731 NI
Wall Sconce
NOT TO SCALE



C | 45734 NI

MATCHING COLLECTION

See entire Serina
Collection on
pages 288-289.



SERINA

	ITEM #	FINISH	INCAND. BULB	W	H	EXT.	HCWO	NOTES
A	45732	NI	(2) 100W (M)	14.5	8	6.25	5.75	Ⓧ (23-30W CFL) May be installed with glass up or down.
B	45733	NI	(3) 100W (M)	22.5	8	6.25	5.5	Ⓧ (23-30W CFL) May be installed with glass up or down.
C	45734	NI	(4) 100W (M)	31	8	6.25	5.5	Ⓧ (23-30W CFL) May be installed with glass up or down.
D	45731	NI	(1) 100W (M)	5.5	9	6.25	5.75	Ⓧ (23-30W CFL) May be installed with glass up or down.

Measurements shown in inches. U.S. & Canada Patent Pending.

LANGFORD™

BRUSHED NICKEL FINISH WITH
SATIN ETCHED WHITE GLASS



A | 5388 NI
Wall Sconce
NOT TO SCALE



B | 8044 NI
Flush Mount



C | 5389 NI



D | 5390 NI



E | 5391 NI

MATCHING COLLECTION

See entire Langford™
Collection on
pages 292-293.



LANGFORD™

ITEM #	FINISH	INCAND. BULB	W	H	EXT.	HCWO	NOTES	
A	5388	NI	(1) 100W (M)	7.25	8	8.25	4.50	ⓓ (9-13W CFL) May be installed on wall with glass up or down.
B	8044	NI	(2) 75W (M) ✦	13	6	---	---	
C	5389	NI	(2) 100W (M)	17.75	8.5	8.25	6.25	ⓓ (9-13W CFL) May be installed on wall with glass up or down.
D	5390	NI	(3) 100W (M)	26.25	8.5	8.25	6.25	ⓓ (9-13W CFL) May be installed on wall with glass up or down.
E	5391	NI	(4) 100W (M)	35	8.5	8.25	6.25	ⓓ (9-13W CFL) May be installed on wall with glass up or down.

Measurements shown in inches.

LANGFORD™

OLDE BRONZE® FINISH WITH
SATIN ETCHED WHITE GLASS



A | 8044 OZ
Flush Mount



B | 5389 OZ



E | 5388 OZ
Wall Sconce
NOT TO SCALE



C | 5390 OZ



D | 5391 OZ

MATCHING COLLECTION

See entire Langford™
Collection on
pages 292-293.



LANGFORD™

ITEM #	FINISH	INCAND. BULB	W	H	EXT.	HCWO	NOTES
A	8044 OZ	(2) 75W (M) ✦	13	6	---	---	
B	5389 OZ	(2) 100W (M)	17.75	8.5	8.25	6.25	Ⓧ (9-13W CFL) May be installed on wall with glass up or down.
C	5390 OZ	(3) 100W (M)	26.25	8.5	8.25	6.25	Ⓧ (9-13W CFL) May be installed on wall with glass up or down.
D	5391 OZ	(4) 100W (M)	35	8.5	8.25	6.25	Ⓧ (9-13W CFL) May be installed on wall with glass up or down.
E	5388 OZ	(1) 100W (M)	7.25	8	8.25	4.5	Ⓧ (9-13W CFL) May be installed on wall with glass up or down.

Measurements shown in inches.

JOLIE

POLISHED CHROME FINISH WITH
SATIN ETCHED GLASS



A | 45637 CH
Wall Sconce
NOT TO SCALE



B | 45638 CH



C | 45639 CH



D | 45640 CH

MATCHING COLLECTION

See entire Jolie
Collection on
pages 306-307.



JOLIE

	ITEM #	FINISH	INCAND. BULB	W	H	EXT.	HCWO	NOTES
A	45637	CH	(1) 100W (M)	5	9	6.25	4.25	Ⓧ (23-30W CFL) May be installed on wall with glass up or down.
B	45638	CH	(2) 100W (M)	13	9.25	8	4.75	Ⓧ (23-30W CFL) May be installed on wall with glass up or down.
C	45639	CH	(3) 100W (M)	20.25	9.25	8	4.75	Ⓧ (23-30W CFL) May be installed on wall with glass up or down.
D	45640	CH	(4) 100W (M)	28	9	8	4.75	Ⓧ (23-30W CFL) May be installed on wall with glass up or down.

Measurements shown in inches.

JOLIE

BRUSHED NICKEL FINISH WITH
SATIN ETCHED GLASS



A | 45638 NI



B | 45639 NI



C | 45640 NI



D | 45637 NI
Wall Sconce
NOT TO SCALE

MATCHING COLLECTION

See entire Jolie
Collection on
pages 306-307.



JOLIE

	ITEM #	FINISH	INCAND. BULB	W	H	EXT.	HCWO	NOTES
A	45638	NI	(2) 100W (M)	13	9.25	8	4.75	Ⓧ (23-30W CFL) May be installed on wall with glass up or down.
B	45639	NI	(3) 100W (M)	20.25	9.25	8	4.75	Ⓧ (23-30W CFL) May be installed on wall with glass up or down.
C	45640	NI	(4) 100W (M)	28	9	8	4.75	Ⓧ (23-30W CFL) May be installed on wall with glass up or down.
D	45637	NI	(1) 100W (M)	5	9	6.25	4.25	Ⓧ (23-30W CFL) May be installed on wall with glass up or down.

Measurements shown in inches.

JOLIE

OLDE BRONZE® FINISH WITH
SATIN ETCHED GLASS



A | 45637 OZ
Wall Sconce
NOT TO SCALE



B | 45638 OZ



C | 45639 OZ



D | 45640 OZ

MATCHING COLLECTION

See entire Jolie
Collection on
pages 306-307.



JOLIE

	ITEM #	FINISH	INCAND. BULB	W	H	EXT.	HCWO	NOTES
A	45637	OZ	(1) 100W (M)	5	9	6.25	4.25	ⓓ (23-30W CFL) May be installed on wall with glass up or down.
B	45638	OZ	(2) 100W (M)	13	9.25	8	4.75	ⓓ (23-30W CFL) May be installed on wall with glass up or down.
C	45639	OZ	(3) 100W (M)	20.25	9.25	8	4.75	ⓓ (23-30W CFL) May be installed on wall with glass up or down.
D	45640	OZ	(4) 100W (M)	28	9	8	4.75	ⓓ (23-30W CFL) May be installed on wall with glass up or down.

Measurements shown in inches.

ARMIDA™

OLDE BRONZE® FINISH WITH
SATIN ETCHED WHITE GLASS



A | 45375 OZ
45375 OZFL



B | 45376 OZ
45376 OZFL



D | 45374 OZ
Wall Sconce
NOT TO SCALE



C | 45377 OZ
45377 OZFL

MATCHING COLLECTION

See entire Armida™
Collection on
pages 300-301.



ARMIDA™

ITEM #	FLOUR. ITEM #	FINISH	INCAND. BULB	FLOUR. BULB	W	H	EXT.	HCWO	NOTES
A	45375	45375 OZFL	OZ	(2) 100W (M) : (2) 13W (GU24)	14	8.75	5.75	6.25	ⓓ (23-30W CFL) May be installed on wall with glass up or down.
B	45376	45376 OZFL	OZ	(3) 100W (M) : (3) 13W (GU24)	23	8.5	5.75	6	ⓓ (23-30W CFL) May be installed on wall with glass up or down.
C	45377	45377 OZFL	OZ	(4) 100W (M) : (4) 13W (GU24)	32.25	9	5.75	6.5	ⓓ (23-30W CFL) May be installed on wall with glass up or down.
D	45374	---	OZ	(1) 100W (M) : ---	5	10.75	7.25	7	ⓓ (23-30W CFL) May be installed on wall with glass up or down.

Measurements shown in inches. U.S. & Canada Patent Pending.

ARMIDA™

POLISHED CHROME FINISH WITH
SATIN ETCHED WHITE GLASS



A | 45374 CH
Wall Sconce
NOT TO SCALE



B | 45375 CH



C | 45376 CH

MATCHING COLLECTION

See entire Armida
Collection on
pages 300-301.



D | 45377 CH

ARMIDA™

	ITEM #	FINISH	INCAND. BULB	W	H	EXT.	HCWO	NOTES
A	45374	CH	(1) 100W (M)	5	10.75	7.25	7	(23-30W CFL) May be installed on wall with glass up or down.
B	45375	CH	(2) 100W (M)	14	8.75	5.75	6.25	(23-30W CFL) May be installed on wall with glass up or down.
C	45376	CH	(3) 100W (M)	23	8.5	5.75	6	(23-30W CFL) May be installed on wall with glass up or down.
D	45377	CH	(4) 100W (M)	32.25	9	5.75	6.5	(23-30W CFL) May be installed on wall with glass up or down.

Measurements shown in inches. U.S. & Canada Patent Pending.

ARMIDA™

BRUSHED NICKEL FINISH WITH
SATIN ETCHED WHITE GLASS



A | 45375 NI
45375 NIFL



B | 45376 NI
45376 NIFL



D | 45374 NI
Wall Sconce
NOT TO SCALE



C | 45377 NI
45377 NIFL

MATCHING COLLECTION

See entire Armida™
Collection on
pages 300-301.



ARMIDA™

ITEM #	FLOUR. ITEM #	FINISH	INCAND. BULB	FLOUR. BULB	W	H	EXT.	HCWO	NOTES
A	45375	45375 NIFL	NI	(2) 100W (M) (2) 13W (GU24)	14	8.75	5.75	6.25	ⓓ (23-30W CFL) May be installed on wall with glass up or down.
B	45376	45376 NIFL	NI	(3) 100W (M) (3) 13W (GU24)	23	8.5	5.75	6	ⓓ (23-30W CFL) May be installed on wall with glass up or down.
C	45377	45377 NIFL	NI	(4) 100W (M) (4) 13W (GU24)	32.25	9	5.75	6.5	ⓓ (23-30W CFL) May be installed on wall with glass up or down.
D	45374	---	NI	(1) 100W (M) ---	5	10.75	7.25	7	ⓓ (23-30W CFL) May be installed on wall with glass up or down.

Measurements shown in inches. U.S. & Canada Patent Pending.

TELFORD™ ENERGY EFFICIENT

BRUSHED NICKEL FINISH WITH
ALABASTER SWIRL GLASS



A | 10604 NI
Wall Sconce
NOT TO SCALE



B | 10608 NI



C | 10609 NI



















D | 10610 NI

MATCHING MIRROR

41011 CH, NI, OZ
See page 413 or
kichler.com.



TELFORD™ ENERGY EFFICIENT

	FLUOR. ITEM #	FINISH	FLUOR. BULB	W	H	EXT.	HCWO	NOTES
A	10604	NI	(1) 13W (GU24)   	7.5	12	9	6	 May be installed on wall with glass up or down.
B	10608	NI	(2) 13W (GU24)   	18.25	10	9	5	 May be installed on wall with glass up or down.
C	10609	NI	(3) 13W (GU24)   	24.75	10	9	5	 May be installed on wall with glass up or down.
D	10610	NI	(4) 13W (GU24)   	33.5	10	9	5	 May be installed on wall with glass up or down.

Measurements shown in inches.

TELFORD™

POLISHED CHROME OR BRUSHED NICKEL FINISH WITH ALABASTER SWIRL GLASS OR OLDE BRONZE® FINISH WITH UMBER ETCHED GLASS



A | 5992 CH, NI, OZ



B | 5993 CH, NI, OZ



D | 5991 CH, NI, OZ
Wall Sconce
NOT TO SCALE



C | 5994 CH, NI, OZ

MATCHING COLLECTION

See entire Telford Collection on pages 310-311.



TELFORD™

	ITEM #	FINISH	INCAND. BULB	W	H	EXT.	HCWO	NOTES
A	5992	CH, NI, OZ	(2) 100W (M)	18	9	9	4	ⓓ May be installed on wall with glass up or down.
B	5993	CH, NI, OZ	(3) 100W (M)	24.75	9	9	4	ⓓ May be installed on wall with glass up or down.
C	5994	CH, NI, OZ	(4) 100W (M)	33.25	9	9	5	ⓓ May be installed on wall with glass up or down.
D	5991	CH, NI, OZ	(1) 100W (M)	7.25	12	9	6	ⓓ May be installed on wall with glass up or down.

Measurements shown in inches.



NICHOLSON™

BRUSHED NICKEL FINISH WITH
SATIN ETCHED GLASS



A | 45881 NI
Wall Sconce
NOT TO SCALE



B | 45882 NI



C | 45883 NI



D | 45884 NI

MATCHING COLLECTION

See entire Nicholson™
Collection on
pages 308-309.



NICHOLSON™

ITEM #	FINISH	INCAND. BULB	W	H	EXT.	HCWO	NOTES
A	45881 NI	(1) 100W (M)	6	10	8.5	5	Ⓧ (18-25W CFL) May be installed on wall with glass up or down.
B	45882 NI	(2) 100W (M)	16	10	8.5	5	Ⓧ (18-25W CFL) May be installed on wall with glass up or down.
C	45883 NI	(3) 100W (M)	24	10	8.5	5	Ⓧ (18-25W CFL) May be installed on wall with glass up or down.
D	45884 NI	(4) 100W (M)	33	10	8.5	5	Ⓧ (18-25W CFL) May be installed on wall with glass up or down.

Measurements shown in inches.

NICHOLSON™

OLDE BRONZE® FINISH WITH
SATIN ETCHED GLASS



A | 45882 OZ



B | 45883 OZ



D | 45881 OZ
Wall Sconce
NOT TO SCALE



C | 45884 OZ

MATCHING COLLECTION

See entire Nicholson™
Collection on
pages 308-309.



NICHOLSON™

	ITEM #	FINISH	INCAND. BULB	W	H	EXT.	HCWO	NOTES
A	45882	OZ	(2) 100W (M)	16	10	8.5	5	Ⓧ (18-25W CFL) May be installed on wall with glass up or down.
B	45883	OZ	(3) 100W (M)	24	10	8.5	5	Ⓧ (18-25W CFL) May be installed on wall with glass up or down.
C	45884	OZ	(4) 100W (M)	33	10	8.5	5	Ⓧ (18-25W CFL) May be installed on wall with glass up or down.
D	45881	OZ	(1) 100W (M)	6	10	8.5	5	Ⓧ (18-25W CFL) May be installed on wall with glass up or down.

Measurements shown in inches.

WEDGEPORT™

BRUSHED NICKEL FINISH WITH SATIN ETCHED
GLASS OR OLDE BRONZE® FINISH WITH
UMBER ETCHED GLASS



A | 5284 NI, OZ
10636 NI, OZ
Wall Sconce
NOT TO SCALE



B | 6086 NI, OZ
Wall Sconce



C | 5285 NI, OZ
10637 NI, OZ



D | 5286 NI, OZ
10638 NI, OZ

MATCHING COLLECTION

See entire Wedgeport™
Collection on
pages 302-303.



MATCHING MIRROR

41011 NI, OZ
See page 413 or
kichler.com.



E | 5287 NI, OZ
10639 NI, OZ

WEDGEPORT™

ITEM #	FLUOR. ITEM #	FINISH	INCAND. BULB	FLUOR. BULB	W	H	EXT.	HCWO	NOTES	
A	5284	NI, OZ	(1) 100W (M)	---	6.25	7.25	8	4.5	Ⓚ (18-25W CFL) May be installed on wall with glass up or down.	
A	---	10636	NI, OZ	---	(1) 13W (GU24) Ⓚ T24	6.25	8	8	4.5	Ⓚ May be installed on wall with glass up or down.
B	6086	NI, OZ	(1) 75W (M) ✓	---	8.5	8.25	4.25	3.5	Ⓚ (18-25W CFL) May be installed on wall with glass up or down.	
C	5285	NI, OZ	(2) 100W (M)	---	15	8.25	8.75	6	Ⓚ (18-25W CFL) May be installed on wall with glass up or down.	
C	---	10637	NI, OZ	---	(2) 13W (GU24) Ⓚ T24	15	8.25	8.75	6.75	Ⓚ May be installed on wall with glass up or down.
D	5286	NI, OZ	(3) 100W (M)	---	23.25	8.25	8.75	2.25	Ⓚ (18-25W CFL) May be installed on wall with glass up or down.	
D	---	10638	NI, OZ	---	(3) 13W (GU24) Ⓚ T24	23.5	9	8.75	2.5	Ⓚ May be installed on wall with glass up or down.
E	5287	NI, OZ	(4) 100W (M)	---	32	8.75	8.75	6	Ⓚ (18-25W CFL) May be installed on wall with glass up or down.	
E	---	10639	NI, OZ	---	(4) 13W (GU24) Ⓚ T24	32	9.5	8.75	6.75	Ⓚ May be installed on wall with glass up or down.

Measurements shown in inches.

DOVER™

BRUSHED NICKEL OR TANNERY BRONZE™
FINISH WITH ETCHED SEEDED GLASS



A | 6322 NI, TZ



B | 6323 NI, TZ



D | 6324 NI, TZ



C | 6719 NI, TZ
Wall Sconce
NOT TO SCALE

MATCHING COLLECTION

See entire Dover™
Collection on
pages 314-316.



MATCHING MIRROR

41011 NI
See page 413 or
kichler.com.



DOVER™

	ITEM #	FINISH	INCAND. BULB	W	H	EXT.	HCWO	NOTES
A	6322	NI, TZ	(2) 100W (M)	14	9	8	6.5	ⓓ May be installed on wall with glass up or down.
B	6323	NI, TZ	(3) 100W (M)	22.5	8	8	5.75	ⓓ May be installed on wall with glass up or down.
C	6719	NI, TZ	(1) 100W (M)	6.25	6.5	6.75	4.25	ⓓ May be installed on wall with glass up or down.
D	6324	NI, TZ	(4) 100W (M)	30.5	9	8	6.25	ⓓ May be installed on wall with glass up or down.

Measurements shown in inches.



ANSONIA™

POLISHED CHROME, BRUSHED NICKEL,
OR OLDE BRONZE® FINISH
WITH SATIN ETCHED GLASS



A | 5446 NI
Wall Sconce
NOT TO SCALE



B | 5447 CH, NI, OZ



C | 5448 CH, NI, OZ



D | 5449 CH, NI, OZ

MATCHING MIRROR

41011 NI
See page 413 or
kichler.com.



MATCHING COLLECTION

See entire Ansonia™
Collection on
pages 312-313.



ANSONIA™

	ITEM #	FINISH	INCAND. BULB	W	H	EXT.	HCWO	NOTES
A	5446	NI	(1) 100W (M)	5.5	9.25	5.5	2.75	Ⓧ (9-13W CFL) May be installed on wall with glass up or down.
B	5447	CH, NI, OZ	(2) 100W (M)	14.75	8.75	5.5	2.75	Ⓧ (9-13W CFL) May be installed on wall with glass up or down.
C	5448	CH, NI, OZ	(3) 100W (M)	23	8.75	5.5	2.75	Ⓧ (9-13W CFL) May be installed on wall with glass up or down.
D	5449	CH, NI, OZ	(4) 100W (M)	31.25	8.75	5.5	2.75	Ⓧ (9-13W CFL) May be installed on wall with glass up or down.

Measurements shown in inches.

BATH & VANITY

BRUSHED NICKEL OR POLISHED CHROME FINISH



A | 6293 NI

Alabaster Swirl Glass



B | 6483 CH



Opal Etched Glass

C | 5150 NI



D | 5151 NI

MATCHING MIRROR

41011 NI
See page 413 or
kichler.com.



BATH & VANITY

ITEM #	FINISH	INCAND. BULB	W	H	EXT.	HCWO	NOTES
A	6293 NI	(3) 100W (M)	24	10.5	8.5	2.75	Ⓧ May be installed on wall with glass up or down.
B	6483 CH	(3) 100W (M)	24	10.5	8.5	2.75	Ⓧ May be installed on wall with glass up or down.
C	5150 NI	(3) 100W (M)	21.75	8.5	7.25	6.25	Ⓧ (9-13W CFL) May be installed on wall with glass up or down.
D	5151 NI	(4) 100W (M)	30	8.5	7.25	2.25	Ⓧ (9-13W CFL) May be installed on wall with glass up or down.

Measurements shown in inches.



BATH & VANITY

POLISHED CHROME OR BRUSHED NICKEL FINISH
WITH OPAL GLASS



A | 6121 CH, NI
Wall Sconce
NOT TO SCALE



Cased Opal Glass

B | 6122 CH, NI



C | 6123 CH, NI



D | 6124 CH, NI

BATH & VANITY

ITEM #	FINISH	INCAND. BULB	W	H	EXT.	HCWO	NOTES	
A	6121	CH, NI	(1) 100W (M)	5	8.75	7.75	5.75	Ⓧ May be installed on wall with glass up or down.
B	6122	CH, NI	(2) 100W (M)	13.5	8.5	6.75	3.75	Ⓧ May be installed on wall with glass up or down.
C	6123	CH, NI	(3) 100W (M)	18	8.75	9.25	3.25	Ⓧ May be installed on wall with glass up or down.
D	6124	CH, NI	(4) 100W (M)	25.5	8.5	10.25	3.25	Ⓧ May be installed on wall with glass up or down.

Measurements shown in inches.

BATH & VANITY

BRUSHED NICKEL, POLISHED CHROME
OR TANNERY BRONZE™ FINISH
WITH ALABASTER SWIRL GLASS



A | 5336 CH, NI, TZ



B | 5337 CH, NI, TZ



C | 5338 CH, NI, TZ



E | 5334 CH, NI, TZ
Wall Sconce
NOT TO SCALE



Alabaster Swirl Glass

D | 5339 CH, NI, TZ

BATH & VANITY

ITEM #	FINISH	INCAND. BULB	W	H	EXT.	HCWO	NOTES
A	5336 CH, NI, TZ	(2) 100W (M)	12.25	8	8	3.5	Ⓧ (9-13W CFL) May be installed on wall with glass up or down.
B	5337 CH, NI, TZ	(3) 100W (M)	24	8	8	3.5	Ⓧ (9-13W CFL) May be installed on wall with glass up or down.
C	5338 CH, NI, TZ	(4) 100W (M)	30	8	8	3.5	Ⓧ (9-13W CFL) May be installed on wall with glass up or down.
D	5339 CH, NI, TZ	(5) 100W (M)	36	8	8	3.5	Ⓧ (9-13W CFL) May be installed on wall with glass up or down.
E	5334 CH, NI, TZ	(1) 100W (M)	5.25	8	8	4.25	Ⓧ (9-13W CFL) May be installed on wall with glass up or down.

Measurements shown in inches.



WALL SCONCE ENERGY EFFICIENT

BRUSHED NICKEL FINISH
OR OLDE BRONZE® FINISH

Satin Etched
Cased Opal Glass



MULTI-POSITIONAL BATH FIXTURE

Create two distinct lighting options with one
fixture: fixture can be installed on the wall
horizontally or vertically.

A | 10670 NI, OZ
Linear Bath
ADA Compliant

Amber Linen
Glass



10670 OZ Shown
Vertically as Wall Sconce

WALL SCONCE ENERGY EFFICIENT

FLUOR. ITEM #	FINISH	FLUOR. BULB	W	H	EXT.	HCWO	NOTES
A 10670	NI, OZ	(2) 13W (GU24)	5	16.5	4	8.25	NI: Satin Etched Cased Opal Glass, OZ: Amber Linen Glass.

Measurements shown in inches.

BATH & VANITY

BRUSHED NICKEL, POLISHED CHROME
OR TANNERY BRONZE™ FINISH



B | 5017 CH, NI, TZ



A | 5003 CH, NI, TZ



C | 5018 CH, NI, TZ



D | 5019 CH, NI, TZ

BATH & VANITY

ITEM #	FINISH	INCAND. BULB	W	H	EXT.	HCWO	NOTES
A 5003	CH, NI, TZ	(3) 60W (M)	18	4.75	6	2.25	(13-15W CFL) G-25 lamp recommended.
B 5017	CH, NI, TZ	(4) 60W (M)	24	4.75	6	2.25	(13-15W CFL) G-25 lamp recommended.
C 5018	CH, NI, TZ	(6) 60W (M)	36	4.75	6	2.25	(13-15W CFL) G-25 lamp recommended.
D 5019	CH, NI, TZ	(8) 60W (M)	48	4.75	6	2.25	(13-15W CFL) G-25 lamp recommended.

Measurements shown in inches.

BATH & VANITY

BRUSHED NICKEL OR
POLISHED CHROME FINISH



A | 623 CH, NI



B | 624 CH, NI



C | 625 CH, NI



D | 626 CH, NI



E | 628 CH, NI

BATH & VANITY


	ITEM #	FINISH	INCAND. BULB	W	H	EXT.	HCWO	NOTES
A	623	CH, NI	(3) 60W (M)	18	4.5	5.5	2.25	(13-15W CFL) G-25 lamp recommended.
B	624	CH, NI	(4) 60W (M)	24	4.5	5.5	2.25	(13-15W CFL) G-25 lamp recommended.
C	625	CH, NI	(5) 60W (M)	30	4.5	5.5	2.25	(13-15W CFL) G-25 lamp recommended.
D	626	CH, NI	(6) 60W (M)	36	4.5	5.5	2.25	(13-15W CFL) G-25 lamp recommended.
E	628	CH, NI	(8) 60W (M)	48	4.5	5.5	2.25	(13-15W CFL) G-25 lamp recommended.

Measurements shown in inches.



NOBU™ ENERGY EFFICIENT

BRUSHED NICKEL FINISH WITH
MATTE WHITE ACRYLIC DIFFUSER



Sandblasted
Outer Glass with
White Inside

Matte White
Acrylic Diffuser

A | **10620 NI**
Wall Sconce
ADA Compliant

B | **10414 NI**
Linear Bath
ADA Compliant

C | **10415 NI**
Linear Bath
ADA Compliant

D | **10416 NI**
Linear Bath
ADA Compliant

NOBU™ ENERGY EFFICIENT

	FLUOR. ITEM #	FINISH	FLUOR. BULB	W	H	EXT.	HCWO	NOTES
A	10620	NI	(2) 13W (G24Q-1)	13	9.5	4	5	D C Sandblasted Outer Glass with White Inside.
B	10414	NI	(1) 24W (T5,G5)	27.25	4.5	3	2.25	D C
C	10415	NI	(1) 39W (T5,G5)	39	4.5	3	2.25	D C
D	10416	NI	(1) 54W (T5,G5)	50.75	4.5	3	2.25	D C

Measurements shown in inches. U.S. & Canada Patent Pending.

ENERGY EFFICIENT

WHITE ACRYLIC DIFFUSER



A | **10697 WH**



B | **10698 WH**

ENERGY EFFICIENT

	FLUOR. ITEM #	FINISH	FLUOR. BULB	W	H	EXT.	HCWO	NOTES
A	10697	WH	(2) 17W (T8)	26.5	6	4.5	3	D May be installed on the ceiling or on the wall vertically or horizontally.
B	10698	WH	(2) 25W (T8)	38.5	6	4.5	3	D May be installed on the ceiling or on the wall vertically or horizontally.

Measurements shown in inches.

LINEAR BATH ENERGY EFFICIENT

WHITE ACRYLIC DIFFUSER WITH BRUSHED NICKEL TRIM



A | 10329 WH



B | 10330 WH



C | 10331 WH



D | 10335 WH

LINEAR BATH ENERGY EFFICIENT


	FLUOR. ITEM #	FINISH	FLUOR. BULB	W	H	EXT.	HCWO	NOTES
A	10329	WH	(2) 18W (G24Q-1)	18.75	5.75	4.25	2.75	May be installed on the ceiling or on the wall vertically or horizontally.
B	10330	WH	(2) 17W (T8,G13)	25.25	5.75	4.25	2.75	May be installed on the ceiling or on the wall vertically or horizontally.
C	10331	WH	(2) 25W (T8,G13)	37.5	5.75	4.25	2.75	May be installed on the ceiling or on the wall vertically or horizontally.
D	10335	WH	(2) 32W (T8,G13)	50.25	5.75	4.25	2.75	May be installed on the ceiling or on the wall vertically or horizontally.

Measurements shown in inches.





LIGHT BULB REFERENCE

Incandescent and Compact Fluorescent Light Bulbs



Compact Fluorescent Bulbs (CFL)

 Look for this symbol throughout our catalog. This symbol indicates the products best suited for Indoor use with self-ballasted, compact fluorescent lamps sold through electrical distributors and lighting showrooms across the U.S.

 This symbol indicates the product best suited for Outdoor use with self-ballasted, compact fluorescent lamps sold through electrical distributors and lighting showrooms across the U.S.


If a light fixture is connected to a dimmer or 3-way switch, you'll need to use a qualified CFL designed to work in these applications. Make sure to look for CFLs that specify use with dimmers or 3-way switches.

Equivalent Light Output

To determine which qualified CFL light bulbs will provide the same amount of light as your current incandescent light bulbs, consult the following chart:

	INCANDESCENT LIGHT BULBS WATTS (W)	INCANDESCENT MINIMUM LIGHT OUTPUT LUMENS	COMMON CFL LIGHT BULBS WATTS (W)
	40	450	9-13
	60	800	13-15
	75	1,100	18-25
	100	1,600	23-30
	150	2,600	30-52




Light-Emitting Diode (LED)



 Look for this symbol throughout our catalog. This symbol indicates fixtures with an integrated LED light source.

LED Light Fixtures and Dimmer Switches

Refer to our listing of recommended dimmer switches that can be used with our LED light fixtures at: kichler.com/dimming

Fluorescent Lamps

PRODUCT ID	DESCRIPTION	
4013	Replacement Ballast	
4014	Replacement Lamp, PLC 26, G24q-3 Base	
4025	Replacement Lamp, PLC 13, G24q-1 Base	
4026	Replacement Lamp, PLC 18, G24q-2 Base	
4028	Replacement Lamp, 2C T6 40W, G10q Base	
4029	Replacement Lamp, 2C T6 55W, G10q Base	
4030	Replacement Lamp, 2C T6 70W, G10q Base	
4033	Replacement Lamp, 13 Watt Anti-Turn Ballast	
4035	Replacement Ballast, 55W circline, G10q Base	
4036	Replacement Ballast, 70W circline, G10q Base	

PRODUCT ID	DESCRIPTION	
4043	Replacement Lamp, MLS13GUWW, 13W, GU24	
4044	Replacement Lamp, MLS18GUWW, 18W, GU24	
4045	Replacement Lamp, MLS26GUWW, 26W, GU24	
4050	Replacement Lamp, 13 Watt GU24 Squat Bulb	
4051	Replacement Lamp, 18 Watt GU24 Squat Bulb	
4074	Replacement Lamp, 11 Watt GU24 Spiral Bulb	
4075	Replacement Lamp, 18 Watt GU24 Quad Tube Bulb	
4089	Replacement Lamp, 32W Circline Bulb	
4090	Replacement Lamp, 40W Circline Bulb	
4094	Replacement Lamp, 14W Fluorescent Bulb	

Halogen & Krypton Lamps

PRODUCT ID	DESCRIPTION
4355 CLR	Bulb wedge base 5W 12V Xenon
5901 CLR	Clear 50W T-3 Double Contact, Bayonet Base, Tungsten (Suitable for use with all Kichler lights requiring Halogen Lamps)
5902 FST	Frosted 50W GU10 Halogen Lamp
5903 CLR	Clear 100W T-3 Mini-Can Base, Tungsten Halogen Lamp
5904 CLR	Clear 20W T-3 Candelabra Base Krypton Lamp
5904 FST	Frosted 20W T-3 Candelabra Base Krypton Lamp

PRODUCT ID	DESCRIPTION
5905 CLR	Clear 60W T-3 Candelabra Base Krypton Lamp
5907 FST	Frosted 40W T-3 Candelabra Base Krypton Lamp
5908 FST	Frosted 60W G9 Halogen Lamp
5909	50W MR16 Shielded GU10 Lamp
5910 CLR	Clear 75W T-3 Mini-Can Base, Tungsten Halogen Lamp
5911 CLR	E11 75W Mini-can halogen bulb

Decorative Light Bulbs



4071 CLR
60W (M)



5971 CLR
40W (C)

Optional Shades



4086 BG
Beige Fabric Shade
3.5" x 5.5" x 4.75"



4121
Mica Fabric Shade
3.25" x 5" x 4.25"



4122
Clear Seedy Glass
4.5" x 6.5"

ACCESSORIES

Standard Gauge Chain

Chain may be ordered in 3' lengths to supplement existing chain supplied with Kichler® fixtures. To order additional chain, look for the chain recommendations listed for fixtures requiring chain.

2979 PB Polished Brass (LifeBrite™)

2996 AB Antique Brass

2996 ACO Antique Copper

2996 AP Antique Pewter

2996 AVI Anvil Iron

2996 BPT Brushed Pewter

2996 BRSG Brushed Silver and Gold

2996 BST Brown Stone

2996 CH Chrome

2996 CLP Classic Pewter

2996 CMZ Cambridge Bronze

2996 CZ Carré Bronze®

2996 DAW Distressed Antique White

2996 DBK Distressed Black

2996 LZ Legacy Bronze™

2996 MCH Midnight Chrome

2996 MIZ Mission Bronze™

2996 NBR Natural Brass

2996 NI Brushed Nickel

2996 NIP Brushed Nickel Painted

2996 OZ Olde Bronze®

2996 PN Polished Nickel

2996 PSS316 Polished Stainless Steel 316

2996 RT Rust

2996 RVN Ravenna™

2996 SGD Sterling Gold

2996 SMG Smokey Gray

2996 SRM Sunrise Mist

2996 SWZ Shadow Bronze™

2996 TRZ Terrene Bronze

2996 TZ Tannery Bronze™

2996 TZG Tannery Bronze™ with Gold Accents

2996 WMZ Warm Bronze™

2996 WZC Weathered Zinc

Heavy Gauge Chain

4901 ACO Antique Copper

4901 AP Antique Pewter

4901 AVI Anvil Iron

4901 BK Black

4901 BPT Brushed Pewter

4901 BRSG Brushed Silver and Gold

4901 CH Chrome

4901 CMZ Cambridge Bronze

4901 CZ Carré Bronze®

4901 DAW Distressed Antique White

4901 DBK Distressed Black

4901 ESP Espresso

4901 LD Londonderry™

4901 LZ Legacy Bronze™

4901 MIZ Mission Bronze™

4901 NI Brushed Nickel

4901 OZ Olde Bronze®

4901 PN Polished Nickel

4901 RVN Ravenna™

4901 SGD Sterling Gold

4901 SRM Sunrise Mist

4901 SWZ Shadow Bronze™

4901 TRZ Terrene Bronze

4901 TZ Tannery Bronze™

4901 TZG Tannery Bronze™ with Gold Accents

4901 WZC Weathered Zinc

Extra Heavy Gauge Chain

4908 AP Antique Pewter

4908 BK Black

4908 CZ Carré Bronze®

4908 DBK Distressed Black

4908 LD Londonderry™

4908 NI Brushed Nickel

4908 NIP Brushed Nickel Painted

4908 OZ Olde Bronze®

4908 SGD Sterling Gold

4908 SRM Sunrise Mist

4908 TRZ Terrene Bronze™

4908 TZ Tannery Bronze™

4908 TZG Tannery Bronze™ with Gold Accents

4909 AP Antique Pewter

4909 CH Chrome

4909 CZ Carré Bronze®

4909 DBK Distressed Black

4909 NI Brushed Nickel

4909 OZ Olde Bronze®

4909 TZG Tannery Bronze™ with Gold Accents

4930 BK Black

4930 CZ Carré Bronze®

4930 LD Londonderry™

4930 RVN Ravenna™

4930 TZG Tannery Bronze™ with Gold Accents

Decorative Chain

4905 TZ Tannery Bronze®

4912 RVN Ravenna™

4915 TZ Tannery Bronze™

4917 TZ Tannery Bronze™

Outdoor Solid Brass Chain

4927 ACO Antique Copper

4927 AGZ Aged Bronze

4927 AVI Anvil Iron

4927 AZ Architectural Bronze®

4927 BK Black

4927 BKG Black with Gold

4927 BRZ Brushed Bronze

4927 CV Canyon View™

4927 DCO Distressed Copper

4927 GNT Textured Granite

4927 LD Londonderry™

4927 OB Olde Brick®

4927 OZ Olde Bronze®

4927 PL Platinum

4927 PR Prairie Rock™

4927 RST Rustic™

4927 RZ Rubbed Bronze

4927 SS Stainless Steel

4927 TZ Tannery Bronze™

4927 WZC Weathered Zinc

Wall Mount Pendant Assembly

BeautyWrap™ Adapter Kit

4931 NI Brushed Nickel

Ceiling Mount Pendant Suspender Kit

Suspend 2- or 3-mini pendants, even Mini-Chandeliers, over a kitchen island, breakfast nook, or almost anywhere. Kit includes a central outlet box canopy cover and (2) 16-1/2" arms with mounting hardware. It's easy and so versatile – add additional fixtures to create a more modular look!

4900 NI Brushed Nickel

4900 TZ Tannery Bronze™

Hang-Straight Canopy Kit

Maintain the clean look of stem-mounted fixtures on ceilings with slopes of 45° (12:12). Kit includes a canopy, mounting strap and hardware with complete instructions. Convert chain hung fixtures to stem-mounted versions by combining with 2997 and 2999 stem segments. Or, for added design flexibility, alter overall fixture length by removing or adding 12" or 24" stem segments.

3000 BK Black

3000 NI Brushed Nickel

3000 WH White

Stem Segments

To increase the fixture overall length to a maximum of 5-stem segments you may order:

12" Length

2995 AP Antique Pewter

2995 BK Black

2995 CH Chrome

2995 OZ Olde Bronze®

2999 ACO Antique Copper

2999 AP Antique Pewter

2999 AVI Anvil Iron

2999 AZ Architectural Bronze®

2999 BA Black

2999 BK Black

2999 BPT Brushed Pewter

2999 BRSG Brushed Silver and Gold

2999 CH Chrome

2999 CLP Classic Pewter

2999 CMZ Cambridge Bronze

2999 CZ Carré Bronze®

2999 DAW Distressed Antique White

2999 DBK Distressed Black

2999 ESP Espresso

2999 LZ Legacy Bronze™

2999 MBZ Marbled Bronze

2999 MCH Midnight Chrome

2999 MIZ Mission Bronze™

2999 NBR Natural Brass

2999 NI Brushed Nickel

2999 NIP Brushed Nickel Painted

2999 OLZ Oiled Bronze

2999 OZ Olde Bronze®

2999 PN Polished Nickel

2999 PRZ Parisian Bronze™

2999 PSS316 Polished Stainless Steel 316

2999 RS Raw Steel

2999 RT Rust

2999 SBR Shadow Brass

2999 SGD Sterling Gold

2999 SWZ Shadow Bronze

2999 TZ Tannery Bronze™

2999 WH White

2999 WMZ Warm Bronze™

2999 WZC Weathered Zinc

4935 ACO Antique Copper

4935 AP Antique Pewter

4935 AVI Anvil Iron

4935 BK Black

4935 BPT Brushed Pewter

4935 CH Chrome

4935 CLP Classic Pewter

4935 CMZ Cambridge Bronze

4935 DAW Distressed Antique White

4935 DBK Distressed Black

4935 NI Brushed Nickel

4935 OZ Olde Bronze®

4935 PN Polished Nickel

4935 RT Rust

4935 SWZ Shadow Bronze

4935 WMZ Warm Bronze™

4935 WZC Weathered Zinc

24" Length

2997 NI Brushed Nickel


36" Length

3036 NI Brushed Nickel


48" Length

3038 NI Brushed Nickel

LED Retrofit Ceiling Adapter



4145 LED
Retrofit Ceiling Adapter for 43845 WHLED



4146 LED
Retrofit Ceiling Adapter for 43846 WHLED

INDEX

206 NI	388	1784 OZ	292	2085 OZ	303	2702 TZ	355
206 OZ	388	1788 NI	293	2086 NI	302	2713 NI	359
206 WH	388	1788 OZ	293	2086 OZ	302	2713 OB	359
208 WH	388	1789 NI	292	2093 NI	317	2714 NI	353
209 NI	388	1789 OZ	292	2093 OZ	317	2754 NI	355
209 OZ	388	1873 NI	207	2343 NI	201	2771 NI	316
209 WH	388	1873 OZ	204	2343 OZ	203	2771 TZ	316
210 WH	388	1884 NI	207	2344 NI	200	2807 NI	317
216 WH	386	1884 OZ	204	2344 OZ	202	2943 NI	201
623 CH	529	1894 CH	102	2345 NI	201	2943 OZ	203
623 NI	529	1894 NI	104	2345 OZ	203	2955 NI	90
624 CH	529	1894 OZ	106	2346 NI	200	2955 OZ	90
624 NI	529	1896 CH	102	2346 OZ	202		
625 CH	529	1896 NI	104	2347 NI	200	3030 NI	371
625 NI	529	1896 OZ	106	2347 OZ	202	3122 NI	383
626 CH	529	1897 CH	102	2520 NI	315	3122 NIA	383
626 NI	529	1897 NI	104	2520 TZ	315	3122 TZ	383
628 CH	529	1897 OZ	106	2523 NI	315	3275 NI	209
628 NI	529			2523 TZ	315	3275 OZ	205
		2019 AB	315	2640 NI	353	3277 NI	311
1671 NI	209	2019 NI	315	2641 NI	353	3277 OZ	311
1671 OZ	206	2019 TZ	315	2643 NI	353	3278 AP	295
1672 NI	208	2020 AB	315	2655 NI	90	3278 OZ	294
1672 OZ	205	2020 NI	315	2664 OZ	334	3279 AP	295
1673 NI	208	2020 TZ	315	2664 PN	332	3279 OZ	294
1673 OZ	205	2021 NI	315	2665 OZ	334	3293 NI	317
1674 NI	208	2021 TZ	315	2665 PN	332	3293 NIA	317
1674 OZ	205	2022 NI	317	2666 OZ	334	3293 OZ	317
1675 NI	207	2022 TZ	317	2666 PN	332	3293 OZU	317
1675 OZ	204	2031 NI	315	2667 NI	90	3299 CH	102
1687 NI	209	2031 TZ	315	2682 OZ	334	3299 NI	104
1687 OZ	206	2043 NI	90	2682 PN	332	3299 OZ	106
1748 NI	312	2055 NI	90	2691 OZ	334	3345 NI	313
1770 NI	317	2076 NI	310	2691 PN	332	3348 NI	313
1770 TZ	317	2076 OZ	310	2693 NI	317	3349 NI	313
1781 NI	292	2077 NI	310	2693 OZ	317	3384 NI	293
1781 OZ	292	2077 OZ	310	2702 NI	316	3384 OZ	293
1783 NI	293	2084 NI	302	2702 OZ	316	3475 NI	209
1783 OZ	293	2084 OZ	302	2702 TZ	316	3475 OZ	206
1784 NI	292	2085 NI	303	2702 NI	355	3476 NI	311

3476 OZ	311	3898 OZ	107	5097 NIFL.....	495	5339 CH	527
3482 NI	293			5097 OZ	496	5339 NI	527
3482 OZ	293	5003 CH	528	5097 OZFL.....	496	5339 TZ.....	527
3497 CH	102	5003 NI	528	5098 CH	494	5359 NI	411, 474
3497 NI	104	5003 TZ.....	528	5098 NI	495	5360 NI	474
3497 OZ	106	5017 CH	528	5098 NIFL.....	495	5361 NI	474
3502 NI	315	5017 NI	528	5098 OZ	496	5362 NI	474
3502 TZ.....	315	5017 TZ.....	528	5098 OZFL.....	496	5367 CH	472
3584 NI	303	5018 CH	528	5099 CH	494	5368 CH	472
3584 OZ	303	5018 NI	528	5099 NI	495	5369 CH	472
3585 NI	302	5018 TZ.....	528	5099 NIFL.....	495	5370 CH	472
3585 OZ	302	5019 CH	528	5099 OZ	496	5388 NI	293, 510
3587 NI	303	5019 NI	528	5099 OZFL.....	496	5388 OZ	293, 511
3587 OZ	303	5019 TZ.....	528	5150 NI	525	5389 NI	510
3606 AP.....	295	5051 NI	476	5151 NI	525	5389 OZ	511
3606 OZ	294	5052 NI	476	5284 NI	303, 522	5390 NI	510
3620 NI	382	5053 NI	476	5284 OZ	303, 522	5390 OZ	511
3623 NI	316	5054 NI	476	5285 NI	522	5391 NI	510
3623 OZ	316	5076 CH	439	5285 OZ	522	5391 OZ	511
3623 TZ.....	316	5076 NI	209, 440	5286 NI	522	5402 NI	475
3627 NI	382	5076 OZ	206, 441	5286 OZ	522	5403 NI	475
3627 OZ	382	5077 CH	439	5287 NI	522	5404 NI	475
3674 NI	209	5077 NI	440	5287 OZ	522	5436 PN	477
3674 OZ	206	5077 OZ	441	5294 NI	317	5437 PN	477
3677 NI	209	5078 CH	439	5294 OZ	317	5438 PN	477
3677 OZ	206	5078 NI	440	5315 MBZ.....	442	5439 PN	477
3681 NI	293	5078 OZ	441	5316 MBZ.....	442	5446 NI	313, 524
3681 OZ	293	5079 CH	439	5317 MBZ.....	442	5447 CH	524
3694 NI	292, 317	5079 NI	440	5334 CH	527	5447 NI	524
3694 OZ	292, 317	5079 OZ	441	5334 NI	527	5447 OZ	524
3694 NIW	301	5085 CH	439	5334 TZ.....	527	5448 CH	524
3694 OZW	301	5085 NI	440	5336 CH	527	5448 NI	524
3718 NI	383	5085 OZ	441	5336 NI	527	5448 OZ	524
3718 TZ.....	383	5096 CH	103, 494	5336 TZ.....	527	5449 CH	524
3752 NI	355	5096 NI	105, 495	5337 CH	527	5449 NI	524
3797 CH	103	5096 NIFL.....	495	5337 NI	527	5449 OZ	524
3797 NI	105	5096 OZ	107, 496	5337 TZ.....	527	5459 AP.....	443
3797 OZ	107	5096 OZFL.....	496	5338 CH	527	5459 OZ	443
3898 CH	103	5097 CH	494	5338 NI	527	5460 AP.....	443
3898 NI	105	5097 NI	495	5338 TZ.....	527	5460 OZ	443

INDEX

5461 AP.....	443	6144 NI.....	201	7772 OZ.....	441, 521	8116 OZ.....	386
5461 OZ.....	443	6144 OZ.....	203			8116 OZLED.....	381
5462 AP.....	443	6162 CH.....	465	8043 CH.....	103	8206 NI.....	388
5462 OZ.....	443	6162 NI.....	464	8043 NI.....	105	8209 NI.....	388
5927 NI.....	491	6162 OZ.....	464	8043 OZ.....	107	8404 NI.....	387
5927 TZ.....	490	6293 NI.....	525	8044 NI.....	293, 510	8405 NI.....	387
5928 NI.....	491	6312 NI.....	489	8044 OZ.....	293, 511	8405 TZ.....	387
5928 TZ.....	490	6313 NI.....	489	8064 NI.....	316, 389	8406 NI.....	387
5929 NI.....	491	6314 NI.....	489	8064 TZ.....	316, 389	8407 NI.....	387
5929 TZ.....	490	6322 NI.....	523	8065 NI.....	316, 389	8407 TZ.....	387
5966 NI.....	460	6322 TZ.....	523	8065 TZ.....	316, 389	8653 CH.....	316
5967 NI.....	460	6323 NI.....	523	8076 NI.....	311	8653 NI.....	316, 385
5968 NI.....	460	6323 TZ.....	523	8076 OZ.....	311	8653 SC.....	316, 385
5988 CZ.....	488	6324 NI.....	523	8102 NI.....	389	8653 TZ.....	316, 385
5989 CZ.....	488	6324 TZ.....	523	8102 NIFL.....	389	8654 AB.....	316
5990 CZ.....	488	6463 CH.....	465	8102 WH.....	389	8654 CH.....	316
5991 CH.....	519	6463 NI.....	464	8102 WHFL.....	389	8654 NI.....	316, 385
5991 NI.....	311, 519	6463 OZ.....	464	8108 NI.....	385	8654 SC.....	316, 385
5991 OZ.....	311, 519	6464 CH.....	465	8108 OZ.....	385	8654 TZ.....	316, 385
5992 CH.....	519	6464 NI.....	464	8108 TZ.....	385	8655 CH.....	316
5992 NI.....	519	6464 OZ.....	464	8109 NI.....	385	8655 NI.....	316, 385
5992 OZ.....	519	6483 CH.....	525	8109 OZ.....	385	8655 PB.....	316
5993 CH.....	519	6520 CH.....	411	8109 TZ.....	385	8655 SC.....	316, 385
5993 NI.....	519	6520 NI.....	411	8110 NI.....	385	8655 TZ.....	316, 385
5993 OZ.....	519	6520 TZ.....	411	8110 OZ.....	385	8880 NI.....	389
5994 CH.....	519	6521 CH.....	411	8110 TZ.....	385	8880 NIFL.....	385, 389
5994 NI.....	519	6521 NI.....	411	8111 AP.....	386	8880 OZ.....	389
5994 OZ.....	519	6521 TZ.....	411	8111 CH.....	386	8880 WH.....	389
		6719 NI.....	315, 523	8111 NI.....	386	8881 NI.....	389
6016 MBZ.....	400, 442	6719 TZ.....	315, 523	8111 OZ.....	386	8881 NIFL.....	385, 389
6086 NI.....	303, 522	6963 NI.....	90, 464	8112 AP.....	386	8881 OZ.....	389
6086 OZ.....	303, 522			8112 CH.....	386	8881 WH.....	389
6121 CH.....	526	7003 NI.....	389	8112 NI.....	386	8882 NI.....	389
6121 NI.....	526	7050 OZ.....	377	8112 NILED.....	381		
6122 CH.....	526	7050 PN.....	377	8112 OZ.....	386	9044 NI.....	411
6122 NI.....	526	7260 WH.....	389	8112 OZLED.....	381	9148 CV.....	179
6123 CH.....	526	7704 OZ.....	377	8116 AP.....	386	9649 CV.....	179
6123 NI.....	526	7704 PN.....	377	8116 CH.....	386	9651 CV.....	179
6124 CH.....	526	7772 CH.....	439, 519	8116 NI.....	386	9652 CV.....	179
6124 NI.....	526	7772 NI.....	440, 520	8116 NILED.....	381	9809 BK.....	359

9809 OZ	359	10638 OZ	522	10885 NI	390, 493	42061 CMZ.....	216
9809 OZLED	359	10639 NI	522	10886 NI	390, 493	42073 CMZ.....	216
9817 AP.....	389	10639 OZ	522	10898 NI	390	42091 PN	425
9825 CV	179	10640 AZ.....	410			42091 PNLED	424
9834 WH	386	10640 NI	410	41011 CH.....	413	42097 CMZ.....	216
9849 CV	179	10670 NI	407, 528	41011 NBR.....	413	42098 CMZ.....	216
9870 RST	358	10670 OZ	407, 528	41011 NI	413	42099 CMZ.....	216
		10686 PN	409, 425	41011 OZ	413	42121 NI	350
10301 WH	393	10693 PN	407	41056 NI	413	42121 OZ	351
10303 WH	393	10697 WH	393, 530	41067 CH	413	42122 NI	350
10304 WH	393	10698 WH	393, 530	41071 NI	413	42122 OZ	351
10315 WH	393			41071 OZ	413	42123 CH.....	371
10325 NI	375	10740 NI	303	41071 SGD.....	413	42124 OZ	115
10326 NI	375	10740 OZ	303	41096 NI	413	42125 OZ	115
10329 WH	531	10741 NI	302	41096 OZ	413	42126 OZ	115, 400
10330 WH	531	10741 OZ	302	41096 SGD.....	413	42141 CHCLR.....	322
10331 WH	531	10742 NI	302			42141 NICS	320
10335 WH	531	10742 OZ	302	42017 BK	89	42141 OZCLR.....	326
		10743 NI	303	42017 NI	88	42141 OZCS.....	324
10414 NI	530	10743 OZ	303	42018 BK	89	42164 AP.....	376, 470
10415 NI	530	10796 SN	408	42018 NI	88	42164 OZ	376, 471
10416 NI	530			42025 NI	382	42167 NIMER	321
10421 SN	408	10802 SI.....	392	42025 OZ	382	42167 OZMER	325
10425 BA	392	10803 BA	390	42028 CH	237	42173 CH	227
10438 NCH.....	408, 493	10804 BA	390	42029 CH	237	42174 CH	227, 373
10439 NCH.....	408, 493	10824 CP	390	42030 CH	235	42175 CH	226
10448 OZ	407	10827 NI	391	42031 CH.....	235	42190 NI	320
10481 PC	409	10827 OZ	391	42033 OZ	347	42190 OZ	324
		10828 NI	391	42034 CH	237	42195 CH.....	226
10604 NI	409, 518	10828 OZ	391	42035 CH	237	42196 NI	350
10608 NI	518	10835 ESNI	385	42044 CH	323	42196 OZ	351
10609 NI	518	10836 NI	385	42044 NIMER	321	42197 NI	350
10610 NI	518	10836 OZ	385	42044 OZ	327	42197 OZ	351
10620 NI	410, 530	10836 WH	385	42044 OZMER	325	42198 CH	322
10630 PN	410	10837 NI	385	42046 CH	322	42198 OZ	326
10636 NI	303, 409, 522	10839 WH	393	42046 NICS.....	320	42203 NBR.....	397
10636 OZ	303, 409, 522	10847 OZ	392	42046 OZ	326	42213 CH	101
10637 NI	522	10847 SI.....	392	42046 OZCS	324	42214 CH	101
10637 OZ	522	10879 NI	391	42047 CH	323	42216 CH	101
10638 NI	522	10879 OZ	391	42047 OZ	327	42245 NI	354, 383

INDEX

42245 OZ	354, 383	42387 AP	272	42526 OZ	343	42588 NBR	367
42246 NI	354, 383	42387 MIZ	275	42544 CH	242	42588 NI	367
42246 OZ	354, 383	42391 CH	225	42545 CH	242	42588 OZ	367
42257 OZ	127	42396 AP	271	42546 CH	242	42591 NI	340
42266 CH	388	42396 MIZ	273	42547 CLP	85	42591 OZ	340
42266 NI	388	42399 AP	272	42547 OZ	87	42591 SGD	340
42266 OZ	388	42399 MIZ	275	42548 CLP	85	42610 SGD	346
42270 NI	345	42432 AP	363	42548 OZ	87	42611 SGD	346
42270 OZ	345	42434 NI	356, 467	42549 CLP	85	42630 CH	241
42275 NI	354, 387	42436 AP	345	42549 OZ	87	42631 CH	239
42275 OZ	354, 387	42436 OZ	345	42556 BPT	291	42632 CH	241
42276 NI	354, 387	42437 AP	345	42556 OZ	291	42633 CH	239
42276 OZ	354, 387	42437 OZ	345	42557 BPT	291	42634 CH	239, 402
42306 CH	225	42439 OZ	377	42557 OZ	291	42643 DBK	349
42308 OZ	348, 364	42456 CHCLR	323	42559 BPT	291	42644 DBK	349
42324 NI	366	42456 OZCLR	327	42559 OZ	291	42649 NBR	330
42324 OZ	366	42456 OZCP	325	42561 BPT	291	42649 OZ	331
42328 NICS	321	42465 WMZ	213	42561 OZ	291	42649 PN	329
42328 OZCS	324	42466 WMZ	213, 356, 372	42562 BPT	291	42708 OZ	127
42329 NICS	321	42467 WMZ	213, 356, 372	42562 OZ	291	42796 BK	339
42329 OZCS	324	42474 PN	51	42563 BPT	291	42797 BK	339
42359 OZ	361	42475 CHCLR	323	42563 OZ	291	42800 AP	352
42359 WZC	361	42475 NIMER	321	42565 NI	340	42800 BZ	352
42372 NILED	405	42475 OZCLR	327	42565 OZ	340	42844 DAW	348
42379 NI	381	42475 OZMER	325	42565 SGD	340	42854 OZ	124
42379 OZ	381	42476 OZ	263	42566 NI	341	42855 OZ	124
42380 NI	381	42478 OZ	263	42566 OZ	341	42860 CLP	265
42380 OZ	381	42479 WMZ	213	42566 SGD	341	42860 SWZ	269
42381 AP	271	42482 OZ	263	42568 NI	341	42861 CLP	265
42381 MIZ	274	42484 OZ	263, 373	42568 OZ	341	42861 SWZ	267
42382 AP	271	42485 OZ	263	42568 SGD	341	42862 CLP	265
42382 MIZ	274	42486 OZ	263	42579 NBR	330	42862 SWZ	269
42383 AP	271	42505 CH	92	42579 OZ	331	42863 CLP	265
42383 MIZ	274	42505 OZ	93	42579 PN	329	42863 SWZ	267
42384 AP	272, 372	42506 CH	92	42580 NBR	330	42864 CLP	266
42384 MIZ	275, 372	42506 OZ	93	42580 OZ	331	42864 SWZ	269
42385 AP	272	42517 CH	361	42580 PN	329	42865 CLP	266
42385 MIZ	275	42517 NI	361	42585 NBR	330	42865 SWZ	269
42386 AP	272	42517 OZ	361	42585 OZ	331	42866 CLP	266
42386 MIZ	275	42525 OZ	343	42585 PN	329	42866 SWZ	269

42869 NI	132	43059 OZ	120	43163 OZ	285	43227 OZ	287
42869 OZ	135	43060 OZ	121	43163 SGD	281	43230 NI	287
42877 NI	132	43073 NI	301	43164 NI	285	43230 OZ	287
42877 OZ	135	43073 OZ	301	43164 OZ	285	43232 NI	287
42878 NI	132, 365	43074 NI	301	43164 SGD	281	43232 OZ	287
42878 OZ	134, 365	43074 OZ	301	43165 NI	285	43234 NI	287
42879 NI	309	43075 NI	301	43165 OZ	285	43234 OZ	287
42879 OZ	309	43075 OZ	301	43165 SGD	281	43255 DAW	163
42880 NI	309	43076 NI	301	43166 NI	285	43256 DAW	163
42880 OZ	309	43076 OZ	301	43166 OZ	285	43257 DAW	163
42881 NI	308, 355	43077 NI	301	43166 SGD	281	43258 DAW	163
42881 OZ	308, 355	43077 NIFL	301	43167 NI	283	43259 DAW	163
42881 OZU	355	43077 OZ	301	43167 OZ	283	43265 DAW	163
42882 NI	308	43105 CLP	347	43167 SGD	278	43275 NBR	49
42882 OZ	308	43105 OZ	347	43169 NI	285	43276 NBR	49
42883 NI	309	43106 CLP	347	43169 OZ	285	43301 NI	77
42883 OZ	309	43106 OZ	347	43169 SGD	281	43301 OZ	74
42884 NI	308	43107 CLP	347	43170 NI	285, 403, 486	43303 NI	77
42884 OZ	308	43107 OZ	347	43170 OZ	285, 403, 485	43303 OZ	73
42885 NI	308	43118 NBR	43	43170 SGD	281, 487	43304 NI	77
42885 OZ	308	43119 NBR	43	43185 AUB	139	43304 OZ	73
42886 OZ	165, 167	43121 CH	243	43186 AUB	140	43305 NI	77
42887 OZ	165, 167	43124 CH	243	43189 AUB	140	43305 OZ	74
42888 OZ	165, 167	43127 NBR	364	43190 AUB	139	43306 NI	75
42890 NI	131	43155 NI	283	43191 AUB	140	43306 OZ	73
42890 OZ	133	43155 OZ	283	43192 NI	283	43318 OZ	114
42891 NI	132, 383	43155 SGD	278	43192 OZ	283	43320 OZ	114
42891 OZ	134, 383	43156 NI	283	43192 SGD	278	43322 DAG	155
42920 CLP	219	43156 OZ	283	43193 AUB	139	43324 DAG	155
42921 CLP	219	43156 SGD	278	43200 OZ	356, 363	43327 DAG	153
42923 CLP	219	43158 NI	283	43201 OZ	356, 363	43328 DAG	155
42940 CLP	94	43158 OZ	283	43223 NI	287	43330 OZ	277
42941 CLP	94	43158 SGD	278	43223 OZ	287	43331 OZ	277
42942 CLP	94, 399	43159 NI	283	43224 NI	287	43332 OZ	277
42943 CHLED	405	43159 OZ	283	43224 OZ	287	43333 OZ	277
42951 CH	353	43159 SGD	278	43225 NI	287	43334 OZ	277, 401
42952 CH	353	43162 NI	285	43225 OZ	287	43346 CLP	223
		43162 OZ	285	43226 NI	287	43347 CLP	223
43057 OZ	121	43162 SGD	281	43226 OZ	287	43348 CLP	223
43058 OZ	121	43163 NI	285	43227 NI	287	43349 CLP	223

INDEX

43352 RT.....	349	43509 NI	298	43601 WZC.....	123	43638 OZ	306
43362 NBR.....	48	43509 OZ	298	43602 WZC.....	123,364	43639 NI	306
43363 NBR.....	48, 397	43511 NI	299	43603 WZC.....	123, 401	43639 OZ	306
43364 CLP.....	71	43511 OZ	299	43607 SGD.....	253	43640 NI	307
43365 CLP.....	71	43512 NI	298	43608 SGD.....	253	43640 OZ	307
43366 CLP.....	71	43512 OZ	298	43609 SGD.....	253	43641 NI	307
43370 OZ	215	43519 DAG.....	349	43610 SGD.....	253	43641 OZ	307
43371 OZ	215, 372	43520 DAG.....	349	43612 CLP.....	346	43649 CHLED.....	381
43373 OZ	215	43537 NI	342	43612 OZ	346	43650 CHLED.....	381
43375 CLP.....	396	43538 NI	342	43613 CLP.....	346	43651 AP.....	304
43375 NBR.....	396	43551 CLP.....	364	43613 OZ	346	43651 OZ	304
43376 CLP.....	396	43551 NBR.....	364	43615 WZC.....	159, 161	43652 AP.....	304
43376 NBR.....	396	43552 NI	338	43616 WZC.....	159, 161	43652 OZ	304
43390 OZ	74	43553 NI	338	43617 WZC.....	159, 161	43653 AP.....	305
43390 NI	77	43563 SBR	344	43618 WZC.....	159, 161	43653 OZ	305
43419 DBK.....	147	43563 SNI	344	43619 SGD.....	251	43654 AP.....	305
43420 DBK.....	147	43564 SBR	344	43620 SGD.....	251	43654 OZ	305
43422 OZ	168	43564 SNI	344	43621 SGD.....	251	43655 AP.....	304
43423 OZ	168	43565 OZ	261	43622 SGD.....	251	43655 OZ	304
43424 OZ	168	43565 SGD.....	257, 259	43623 SGD.....	251, 402	43656 AP.....	305
43433 AUB	145	43566 OZ	261	43624 NI	199, 373	43656 OZ	305
43435 AUB	145	43566 SGD.....	257, 259	43625 NI	199, 373	43657 AP.....	305
43436 AUB	145, 401	43567 OZ	261	43627 NI	199	43657 OZ	305
43437 NI	221	43567 SGD.....	257, 259	43628 NI	199	43664 NI	297
43438 NI	221	43568 OZ	261, 373	43629 NI	199, 373	43664 OZ	297
43442 NI	221	43568 SGD.....	257, 259, 373	43630 BK	289	43665 NI	297
43451 SGD.....	249	43569 OZ	261	43630 NI	289	43665 OZ	297
43452 SGD.....	249	43569 SGD.....	257, 259	43631 BK	289	43666 NI	296
43457 OZ	120	43570 OZ	261, 402	43631 NI	289	43666 OZ	296
43486 NIBL	363	43570 SGD.....	257, 259, 402	43632 BK	289	43667 NI	296
43488 OZ	363	43580 CH	79	43632 NI	289	43667 OZ	296
43489 BKGLD.....	363	43580 NBR.....	78	43634 BK	289	43668 NI	297
43489 BKSLV.....	363	43581 AVI.....	157	43634 NI	289	43668 OZ	297
43491 AUB	143	43582 AVI.....	157	43635 BK	289	43669 NI	297
43503 NI	299	43584 AVI.....	157, 365	43635 NI	289	43669 OZ	297
43503 OZ	299	43586 AVI.....	157	43636 BK	289	43670 NI	109
43504 NI	299	43587 NBR.....	119	43636 NI	289	43670 OZ	109
43504 OZ	299	43588 RT.....	352	43637 NI	307	43671 NI	108
43506 NI	298	43589 NBR.....	119, 365	43637 OZ	307	43671 OZ	108
43506 OZ	298	43600 WZC.....	123, 348	43638 NI	306	43672 NI	108


43672 OZ 108	43717 RS 117, 348	43764 OZ 335	43825 WZC..... 171, 400
43674 NI 109	43718 RS 117	43764 PN 333	43826 WZC..... 171
43674 OZ 109	43719 RS 117, 365	43765 OZ 335	43839 NBR..... 55
43675 NI 109	43723 ESP..... 231, 233	43765 PN 333	43839 CLP..... 57
43675 OZ 109	43724 ESP..... 231, 233	43766 OZ 335	43841 NBR..... 55
43676 OZ 125	43725 ESP..... 231, 233	43766 PN 333	43841 CLP..... 57
43677 OZ 125	43726 ESP..... 231, 233	43767 OZ 335	43843 NBR..... 55
43678 OZ 125	43727 ESP..... 231, 233, 402	43767 PN 333	43843 CLP..... 57
43680 WH 45, 46	43728 SGD 255	43768 OZ 335	43845 WHLED27 381
43682 WH 45, 47, 371	43729 SGD 255	43768 PN 333	43845 WHLED30 381
43683 WH 45, 47	43731 OZ 211	43770 AGZ 175	43846 WHLED27 381
43686 NI 69	43732 OZ 211	43771 AGZ 175	43846 WHLED30 381
43687, NI..... 69	43733 OZ 211	43772 AGZ 175	43850 CH 368
43688 NI 69	43734 OZ 211	43773 AGZ 175	43850 NI 368
43689 NI 69	43737 CLP..... 137, 328	43774 AVI..... 149, 151	43850 OZ 368
43690 SGD 251	43737 NBR..... 136, 328	43775 AVI..... 149, 151	43851 CH 369
43700 CLP..... 191	43738 CLP..... 137, 328	43776 AVI..... 149, 151	43851 NI 369
43700 NBR..... 185, 188	43738 NBR..... 136,328	43777 AVI..... 149, 151, 398	43851 OZ 369
43701 CLP..... 191	43739 CLP..... 137, 328	43779 AGZ 173	43852 CH 369
43701 NBR..... 185, 188	43739 NBR..... 136, 328	43783 NBR..... 83, 337	43852 NI 369
43702 CLP..... 191	43740 CLP..... 137	43783 OZ 81, 337	43852 OZ 369
43702 NBR..... 185, 187	43740 NBR..... 136	43783 PN 82, 337	43853 CH 368
43703 CLP..... 191	43741 CLP..... 137	43784 NBR..... 83, 336	43853 NI 368
43703 NBR..... 185, 187	43741 NBR..... 136	43784 OZ 81, 336	43853 OZ 368
43704 CLP..... 189	43742 NBR..... 63	43784 PN 82, 336	43857 NBR..... 97
43704 NBR..... 185, 187	43743 NBR..... 63	43785 NBR..... 83, 336	43857 SN 99
43705 CLP..... 191	43744 NBR..... 63	43785 OZ 81, 336	43859 NBR..... 97
43705 NBR..... 185, 188	43745 OZ 229	43785 PN 82, 336	43859 SN 99
43706 CLP..... 193, 195	43747 OZ 229	43787 NBR..... 83, 397	43875 NILED 381
43706 OZ 197	43748 OZ 229	43787 OZ 81, 397	43875 OZLED 381
43707 CLP..... 193, 195	43749 OZ 229	43787 PN 82, 397	43876 NILED 381
43707 OZ 197	43750 OZ 229	43792 NI 356	43876 OZLED 381
43709 CLP..... 193, 195	43753 AUB 59, 61	43803 SGD 248	43877 NILED 381
43709 OZ 197	43755 AUB 59, 61, 372	43804 SGD 248	43877 OZLED 381
43710 CLP..... 193, 195, 403	43756 AUB 59, 61, 400	43805 SGD 247	43883 NILED 381
43710 OZ 197, 403	43758 ESP..... 231, 233	43811 SGD 245	43883 OZLED 381
43712 PN 111, 113	43759 NI 41	43812 SGD 245	43883 PNLED 381
43713 PN 111, 113	43760 NI 41	43813 SGD 245	43885 NILED 381
43715 PN 111, 113	43761 NI 41	43823 WZC..... 171	43885 OZLED 381
43716 PN 111, 113	43762 NI 41, 397	43824 WZC..... 171	43885 PNLED 381


INDEX

43900 CLP.....	65	45138 NI	459	45317 CH	463	45377 NI	517
43900 OZ	67	45139 NI	459	45317 NI	462	45377 NIFL.....	517
43901 CLP.....	65	45140 NI	459	45319 CH	463	45377 OZ	515
43901 OZ	67	45149 AP	454	45319 NI	462	45377 OZFL.....	515
43902 CLP.....	65	45149 CH	455	45358 BPT	291, 399, 468	45402 CLP.....	478
43902 OZ	67	45150 AP	454	45358 CH	399, 468	45402 OZ	479
43907 CLP.....	183	45150 CH	455	45358 OZ	291, 399, 468	45403 CLP.....	478
43907 NBR.....	181	45151 AP.....	454	45359 BPT	468	45403 OZ	479
43908 CLP.....	183	45151 CH	455	45359 CH	468	45404 CLP.....	478
43908 NBR.....	181	45152 AP.....	454	45359 OZ	468	45404 OZ	479
43909 CLP.....	183	45152 CH	455	45360 BPT	468	45421 NI	287, 403, 483
43909 NBR.....	181	45161 AP	400, 470	45360 CH	468	45421 OZ	287, 403, 482
43910 CLP.....	183, 398	45161 OZ	400, 471	45360 OZ	468	45422 NI	483
43910 NBR.....	181, 398	45162 AP.....	470	45361 BPT	468	45422 OZ	482
43931 NBR.....	53	45162 OZ	471	45361 CH	468	45423 NI	483
43933 NBR.....	53	45163 AP.....	470	45361 OZ	468	45423 OZ	482
43934 NBR.....	53, 398	45163 OZ	471	45362 CLP.....	266, 403	45424 NI	483
		45164 AP.....	470	45362 SWZ.....	269, 403	45424 OZ	482
45054 NI	486	45164 OZ	471	45371 OZ	444	45431 CH	452
45054 OZ	485	45171 CH	453	45371 SGD.....	445	45432 CH	452
45054 SGD	487	45172 CH	453	45372 OZ	444	45433 CH	452
45055 NI	486	45173 CH	453	45372 SGD.....	445	45434 CH	452
45055 OZ	485	45178 OZ	263, 402	45373 OZ	444	45457 CH	433
45055 SGD.....	487	45190 NI	438	45373 SGD.....	445	45457 OZ	121, 431
45056 NI	486	45193 AP.....	454	45374 CH	516	45458 CH	433
45056 OZ	485	45193 CH	455	45374 NI	301, 517	45458 OZ	431
45056 SGD.....	487	45218 NI	492	45374 NIFL.....	517	45459 CH	433
45086 PN	398, 425	45220 NI	492	45374 OZ	301, 515	45459 OZ	431
45087 PN	425	45281 AP.....	272, 447	45374 OZFL.....	515	45460 CH	433
45087 PNLED	424	45281 MIZ.....	275	45375 CH	516	45460 OZ	431
45088 PN	425	45282 AP.....	447	45375 NI	517	45477 CH	456
45088 PNLED	424	45282 MIZ.....	447	45375 NIFL.....	517	45478 CH	456
45117 NI	438	45283 AP.....	447	45375 OZ	515	45478 NI	457
45118 NI	438	45283 MIZ.....	447	45375 OZFL.....	515	45479 CH	456
45119 NI	438	45284 AP.....	447	45376 CH	516	45479 NI	457
45120 NI	438	45284 MIZ.....	447	45376 NI	517	45480 CH	456
45131 TRZ.....	401	45291 CH	225	45376 NIFL.....	517	45480 NI	457
45132 NI	467	45293 CH	225	45376 OZ	515	45486 CH	480
45133 NI	467	45316 CH	463	45376 OZFL.....	515	45486 ORZ	481
45134 NI	467	45316 NI	462	45377 CH	516	45487 CH	480

45487 ORZ.....	481	45569 CH.....	498	45612 ORZ.....	451	45731 BK.....	289, 508
45488 CH.....	480	45569 NI.....	499	45613 CH.....	450	45731 NI.....	289, 509
45488 ORZ.....	481	45569 OZ.....	497	45613 ORZ.....	451	45732 BK.....	508
45489 CH.....	480	45570 CH.....	498	45614 CH.....	450	45732 NI.....	509
45489 ORZ.....	481	45570 NI.....	499	45614 ORZ.....	451	45733 BK.....	508
45500 CH.....	458	45570 OZ.....	497	45615 CHLED.....	405, 422	45733 NI.....	509
45501 CH.....	458	45571 CH.....	498	45615 OZLED.....	405, 423	45734 BK.....	508
45502 CH.....	458	45571 NI.....	499	45617 CHLED.....	422	45734 NI.....	509
45503 CH.....	458	45571 OZ.....	497	45617 OZLED.....	423	45801 CHLED.....	426
45504 NI.....	299, 506	45572 CH.....	504	45618 CHLED.....	422	45801 OZLED.....	426
45504 OZ.....	299, 507	45572 NI.....	109, 505	45618 OZLED.....	423	45820 CHLED.....	416
45512 NI.....	506	45572 OZ.....	109, 503	45627 PN.....	398, 449	45821 CHLED.....	416
45512 OZ.....	507	45573 CH.....	504	45628 PN.....	449	45822 CHLED.....	416
45513 NI.....	506	45573 NI.....	505	45629 PN.....	449	45823 CHLED.....	416
45513 OZ.....	507	45573 OZ.....	503	45630 PN.....	449	45828 CHLED.....	418
45514 NI.....	506	45574 CH.....	504	45637 CH.....	512	45828 OZLED.....	419
45514 OZ.....	507	45574 NI.....	505	45637 NI.....	307, 513	45829 CHLED.....	418
45542 DAG.....	430	45574 OZ.....	503	45637 OZ.....	307, 514	45829 OZLED.....	419
45543 DAG.....	430	45575 CH.....	504	45638 CH.....	512	45830 CHLED.....	418
45544 DAG.....	430	45575 NI.....	505	45638 NI.....	513	45830 OZLED.....	419
45545 DAG.....	430	45575 OZ.....	503	45638 OZ.....	514	45831 CHLED.....	418
45550 AP.....	304, 501	45576 NI.....	132	45639 CH.....	512	45831 OZLED.....	419
45550 CH.....	500	45576 OZ.....	134	45639 NI.....	513	45836 CHLED.....	426
45550 OZ.....	304, 502	45580 CH.....	79, 399, 436	45639 OZ.....	514	45836 OZLED.....	426
45551 AP.....	501	45580 NBR.....	78, 399, 437	45640 CH.....	512	45838 CHLED.....	426
45551 CH.....	500	45581 CH.....	436	45640 NI.....	513	45838 OZLED.....	426
45551 OZ.....	502	45581 NBR.....	437	45640 OZ.....	514	45839 CHLED.....	426
45552 AP.....	501	45582 CH.....	436	45641 CH.....	473	45839 OZLED.....	426
45552 CH.....	500	45582 NBR.....	437	45642 CH.....	473	45844 CHLED.....	427
45552 OZ.....	502	45583 CH.....	436	45643 CH.....	473	45845 CHLED.....	427
45553 AP.....	501	45583 NBR.....	437	45644 CH.....	473	45846 CHLED.....	427
45553 CH.....	500	45601 CH.....	461	45656 CHLED.....	405, 417	45847 CHLED.....	427
45553 OZ.....	502	45602 CH.....	461	45701 CLP.....	191, 435	45851 CHLED.....	420
45558 CH.....	421	45603 CH.....	461	45701 NBR.....	185, 188, 434	45852 CHLED.....	420
45559 CH.....	421	45604 CHLED.....	405, 428	45702 CLP.....	435	45853 CHLED.....	420
45560 CH.....	421	45605 CHLED.....	428	45702 NBR.....	434	45854 CHLED.....	420
45561 CH.....	421	45606 CHLED.....	428	45703 CLP.....	435		
45568 CH.....	498	45611 CH.....	450	45703 NBR.....	434		
45568 NI.....	296, 499	45611 ORZ.....	451	45704 CLP.....	435		
45568 OZ.....	296, 497	45612 CH.....	450	45704 NBR.....	434		

Legend / Symbol Guide

 = This symbol indicates the product best suited for Indoor use with self-ballasted, compact fluorescent lamps sold through electrical distributors and lighting showrooms across the U.S.

 = This symbol indicates the product best suited for Outdoor use with self-ballasted, compact fluorescent lamps sold through electrical distributors and lighting show rooms across the U.S.

(C) = Candelabra base lamp (E-12).

(C/K) = Candelabra base lamp (E-12) or Krypton candelabra base lamp.

(K) = Krypton candelabra base lamp.


(M) = Medium base lamp (E-26).

(MNCN) = Mini-can base halogen lamp

✓ = Fixture requires supply wire rated for at least 75° C.

❖ = Fixture requires supply wire rated for at least 90° C.

☆ = When electrical connection is made inside the fixture, supply wire must be rated at least 75° C. When electrical connection is made in an outlet box, supply wire must be rated at least 60° C.

 = Installation Instructions: Fixture must be supported independently of the outlet box unless the outlet box is UL listed for the weight to be supported. Consult a qualified electrician/installer. Required installation parts included.

D = Diameter

Ext. = Extension

Fluor. = Fluorescent

H = Height

HCWO = Height from Center of Wall Opening

Incand. = Incandescent


L = Length


Ovrll. H = Overall Height

W = Width


Extra Wire = Extra wire beyond chain and/or stems


Chain/Stem = Length of chain or stem supplied with fixture


 = Title 24 is a document that contains the building codes for the state of California. All lighting fixtures in this catalog that comply with the Aug. 1, 2009 revision of the California Title 24 standards are marked with the T24 logo. For more information, visit www.energy.ca.gov/title24


 = ADA Compliant


 = CFL Lamp Included


 = DAMP

 = Dark Sky Compliant


 = Lamp Included

 = Line Extension

 = LED

 = WET

★ = Kichler® Products are not produced or associated with any Native American Indians, nor are they a Native American product or the product of a particular Indian, Indian tribe or Indian arts and crafts organization as defined by 25 U.S.C. §305 et. seq.

 = Federal Communications Commission, devises designated with this logo comply with part 15 of the FCC Rulest

• Bulbs not included unless otherwise noted.

• Wattages stated are the maximum recommended, however, you may use lower wattage lamps to suit your lighting needs. Some recommended lamps are not available in the maximum allowable wattage.

• All electrical products are rated as 120-volt, AC unless otherwise noted.

• All electrical products are certified and listed to UL/CSA/ETL Standards for use in U.S.A. and Canada except where noted.

• All products featured in the outdoor section are certified and listed to UL/CSA/ETL standards for wet location except where noted.

• All chain drop products equipped with at least 72" of chain unless otherwise noted.

• Many long life tungsten halogen capsule lamps are now available as alternates to conventional incandescent light bulbs. The halogen capsule lamps may be used to replace any lamp of a higher wattage, but not to exceed the existing specified maximum wattage, i.e., 72W may replace a 75W.

• On some products, in order to accommodate higher than normal ceiling height, extra lead wire is supplied and specified. With additional sections of chain or stems (not included), this allows an added measure of design flexibility.

• Finishes for fixtures installed outdoors are subject to change due to prolonged exposure to sunlight, airborne pollutants and other forms of weathering.

• To serve you better, Kichler® reserves the right to make improvements to the products in this catalog. Therefore, some products may change during the life of the catalog and the product information contained in this catalog may also have changed.

Consumer Notice

Federal Legislation to phase out 100 watt Incandescent Bulbs started January 2012

The federal government enacted the Energy Independence and Security Act of 2007 in December 2007, requiring all general-purpose light bulbs that produce 310–2600 lumens of light be 30% more energy efficient (similar to current halogen lamps) than current incandescent bulbs by 2014. The efficiency standards started with 100 watt bulbs in January 2012 and will end with 40 watt bulbs in January 2014.

Light bulbs outside of this range are exempt from the restrictions (historically, less than 40 watts or more than 150 watts). Also exempt are several classes of specialty lights, including appliance lamps, rough service bulbs, 3-way, colored lamps, and plant lights.

By 2020, a second tier of restrictions would become effective; which requires all general-purpose bulbs to produce at least 45 lumens per watt (similar to current CFLs). Exempt from the Act are reflector flood, 3-way, candelabra, colored, and other specialty bulbs.

Many Governments worldwide have passed measures to prohibit the sale of incandescent light bulbs for general lighting. The aim is to encourage use of more energy efficient lighting alternatives, such as compact fluorescent lamps (CFLs) and LED lamps.

References: www.energy.senate.gov

We go to great lengths to assure the metal and glass finishes shown in the catalog match the actual products, but printing variations and variations in chemical finishes and the nature of hand applied finishing will cause some differences between the printed images and actual product, and from one product to another.

We use only non-ferrous materials on the exterior parts of our outdoor lantern products, and use the best available weather-resistant finishes. However, due to some extreme environmental conditions such as acid rain, salt air and ultraviolet exposure, we cannot guarantee our exterior finishes, with the exception of our LifeBrite® lanterns.

Due to environmental conditions such as soil acidity, concrete alkalinity and other corrosive soil and air conditions, we cannot guarantee our direct burial posts.

Abbreviation Key

AB	Antique Brass	CTZ	Colton Bronze™	OZSW	Olde Bronze® with Satin Etched White Glass
ABZ	Antique Bronze	CV	Canyon View™	OZU	Olde Bronze® with Umber Glass
ACK	Antique Crackle™	CZ	Carré Bronze®	OZW	Olde Bronze® with Satin Etched White Glass
ADC	Adobe Cream™	DBK	Distressed Black	PB	Polished Brass
AGZ	Aged Bronze	DBR	Distressed Brass	PBC	Polished Brass with Chrome
AGZS	Aged Bronze with Satin-Etched Cased Opal Glass	DCO	Distressed Copper	PGR	Pebbled Granite™
ANO	Art Nouveau Bronze	DZ	Dore Bronze™	PL	Platinum
AP	Antique Pewter	ESP	Espresso	PN	Polished Nickel
AVI	Anvil Iron	FDS	Feldspar™	PPW	Polished Pewter
AZ	Architectural Bronze™	FZ	Franciscan Bronze™	PR	Prairie Rock™
AZT	Textured Architectural Bronze™	GBR	Golden Brûlée™	PRZ	Parisian Bronze™
BA	Brushed Aluminum	GD	Gold	PSS316	Polished Stainless Steel Marine Grade
BAW	Brushed Aluminum with Wood Trim	GNT	Granite	PZ	Patina Bronze
BAB	Burnished Antique Brass	GST	Galvanized Steel	RBZ	Royal Bronze
BBZ	Burnished Bronze™	HB	Heritage Bronze™	RNX	Rubbed Onyx
BCZ	Burnished Copper Bronze	LBZ	Lincoln Bronze™	RST	Rustic™
BGN	Burnished Granite™	LD	Londonderry™	RVN	Ravenna™
BH	Buckhorn™	LED	Light Emitting Diode	RZ	Rubbed Bronze™
BK	Black	LZ	Legacy Bronze™	RZS	Rubbed Bronze™ with Satin Etched Glass
BKG	Black with Gold Highlights	LZG	Legacy Bronze™ with Gold Accents	SC	Stucco White
BKN	Black Nickel	MBZ	Marbled Bronze	SCK	Seine Crackle™
BKS	Black with Satin-Etched Glass	MCH	Midnight Chrome	SEG	Satin Etched Glass
BKT	Textured Black	MIZ	Mission Bronze™	SGD	Sterling Gold
BKZ	Berkshire Bronze™	MPC	Mottled Pecan™	SGE	Sage
BMB	Brushed Modern Bronze	MUL	Multicolor	SI	Silver
BPT	Brushed Pewter	NBR	Natural Brass	SN	Satin Nickel
BRL	Brûlée™	NCH	Brushed Nickel & Polished Chrome	SRM	Sunrise Mist™
BRZ	Brushed Bronze	NCHB	Brushed Nickel and Polished Chrome with Black	SS	Stainless Steel
BS	Burnished Silver	NI	Brushed Nickel	SWZ	Shadow Bronze™
BSG	Burnished Silver and Gold	NIA	Brushed Nickel with Alabaster Swirl Glass	SZ	Sedona Bronze™
BST	Brown Stone	NIMER	Brushed Nickel with Mercury Glass	TRZ	Terrene Bronze™
BZ	Bronze	NIS	Brushed Nickel with Satin Etched Glass	TZ	Tannery Bronze™
CH	Polished Chrome	NISW	Brushed Nickel with Satin Etched White Glass	TZG	Tannery Bronze™ with Gold
CHCLR	Chrome with Clear Glass	NIW	Brushed Nickel with White Fabric Shade	TZP	Tannery Bronze™ with Polished Brass Accents
CHW	Polished Chrome with Satin-Etched White Glass	OAU	Olde Auburn™	VNB	Vintage Natural Brass™
CLP	Classic Pewter	OB	Olde Brick®	WBR	Wispy Brûlée*
CLR	Clear	OBB	Oil Brushed Bronze™	WCP	Weathered Copper
CMB	Cambridge	OI	Olde Iron	WSP	Weathered Steel
CMZ	Cambridge Bronze	OLZ	Oiled Bronze	WH	White
CP	Champagne	OMC	Olde Mill Copper™	WZC	Weathered Zinc
CPBG	Champagne and Brushed Gold	ORZ	Oil Rubbed Bronze		
CSH	Cashmere™	OZ	Olde Bronze®		
CST	Canyon Slate™	OZCLR	Olde Bronze® with Clear Glass		
		OZMER	Olde Bronze® with Mercury Glass		
		OZS	Olde Bronze® with Satin Etched Glass		

CONNECT WITH US



Become a fan of Kichler Lighting at: [facebook.com, search Kichler Lighting](https://www.facebook.com/kichlerlighting)



Follow us on twitter at: twitter.com/kichlerlight



Find us on Pinterest at: <http://pinterest.com/kichlerstyle/>



Join us on Houzz at: <http://www.houzz.com/pro/kichlerlighting/kichler>



Watch us on [youtube.com/KichlerLighting](https://www.youtube.com/KichlerLighting)

To find an Authorized Dealer, visit: www.kichler.com

KICHLER

World Headquarters
7711 E. Pleasant Valley Rd.
PO Box 318010
Cleveland, Ohio 44131-8010





Featured on Front Cover:
Vance™ Collection
Pendant 43931 NBR, Page 52

Featured on Back Cover:
Mona™ Collection
Wall Sconce 43375 CLP, Page 396

KICHLER.

GET INSPIRED AT
KICHLER.COM
For more information call
866.558.5706

Catalog No. **K116**
www.kichler.com
Printed in USA
15-KD-3452-125M
© Copyright. All rights reserved. Kichler®
The majority of newer Kichler fixtures
are U.S. and Canadian Patent Pending.