

minkaAire®
A Minka Group® Co.



2016

Table of Contents

INTRODUCTION	2-3	Slipstream XXL	26-29, 138-139	Timeless	104-107
CONTEMPORARY COLLECTION		Spacesaver	194-195	Traditional Concept™ 44"	82-83, 156-157
Acero™	88-89	Spectre	38-41	Traditional Concept™ 52"	80-81, 154-155
Aluma	54-55	Strata	164-165	TRADITIONAL COLLECTION	
Aluma Wet	162-163	Symbio	48-49	Bolo	116-117
Artemis™	8-13	Uchiwa	84-85	Calais™	127
Artemis™ XL5	32-33	Wave	60-61	Classica	124-125
Aviation	34-37	Wing	56-57	Classica - Gallery Edition	124
Cirque™	86-87	Xtreme	22-25	Contractor 42"	228-229
Como™	90-91	Zen	92-93	Contractor 52"	226-227
Concept™ I	74-75	TRANSITIONAL COLLECTION		Contractor LED	214-215
Concept™ II 44"	78-79	Airus™	94-95	Contractor Plus	216-217
Concept™ II 52"	76-77	Cage Free Gyro™	130	Contractor Uni-Pack LED	212-213
Concept™ II Wet 52"	152-153	Delano®	98-99	Contractor Uni-Pack with 3-Light	218-219
Concept™ I Wet 52"	150-151	Delano® II	100-101	Contractor Uni-Pack with Light	220-225
Concept™ I Wet 58"	148-149	Dyno	184-185	Craftsman™	180
Flyte®	64-65	Elemental Gyro™	131	Cristafano™	128
Force	4-5	Gauguin™	170-171	Great Room Traditional	118-119
Gilera	68-71	Gyrette™	136	Groton	144-145
Java	52-53, 160-161	Gyro™	134	Iconic™	102-103
Java LED	50-51, 158-159	Gyro™ Wet	135, 168	Lineage™	121
Kewl	62-63	Hilo	192-193	Mesa	230
Light Wave	58-59	Kafé	114-115	Mojo	188-189
Moda	72-73	Kafé-XL	112-113	Mojo II	190-191
Pancake	14-15	Kola	110-111	Napoli™	122
Rainman™	166-167	Kola-XL	108-109	Napoli™ II	123
Raptor	6-7	New Era	96-97	Retro Style Fan	196
Roto	44-45	Ninety-Nine	16-21	Santa Lucia™	120
Roto XL	146-147	Rudolph	182-183	Sundance™	178-179
Sabot	46-47	Shangri-La®	169	Sundowner®	174-177
San Francisco®	66-67	Simple	42-43, 142-143	Supra® 32"	210-211
Slipstream	30-31, 140-141	Sunseeker	172-173	Supra® 44"	208-209

The products depicted in this catalog are protected by United States Federal and/or State Law, including Patent, Trademark and/or Copyright Laws.

Catalog and all elements of catalog design are protected by United States Federal and/or State Law, including Patent, Trademark and/or Copyright Laws.

Supra® 44" with Light 206-207
 Supra® 52" 202-205
 Supra® 52" with Light 200-201
 Traditional Gyro™ 129
 Traditional Mojo 186-187
 Ultra-Max™ 198-199
 Vintage Gyro™ 132-133
 Volterra™ 126

GYRO™ COLLECTION

Cage Free Gyro™ 130
 Elemental Gyro™ 131
 Gyrette™ 136
 Gyro™ 134
 Gyro™ Wet 135-168
 Traditional Gyro™ 129
 Vintage Gyro™ 132-133

INDOOR/OUTDOOR COLLECTION

Aluma Wet 162-163
 Concept™ II Wet 52" 152-153
 Concept™ I Wet 52" 150-151
 Concept™ I Wet 58" 148-149
 Craftsman™ 180
 Gauguin™ 170-171
 Groton 144-145
 Gyro™ Wet 135, 168
 Java 52-53, 160-161
 Java LED 50-51, 158-159
 Rainman™ 166-167
 Roto XL 146-147
 Shangri-La® 169
 Simple 42-43, 142-143

Slipstream 30-31, 140-141
 Slipstream XXL 26-29, 138-139
 Strata 164-165
 Sundance™ 178-179
 Sundowner® 174-177
 Sunseeker 172-173
 Traditional Concept™ 44" 82-83, 156-157
 Traditional Concept™ 52" 80-81, 154-155

VALUE COLLECTION

Dyno 184-185
 Hilo 192-193
 Mojo 188-189
 Mojo II 190-191
 Retro Style Fan 196
 Rudolph 182-183
 Spacesaver 194-195
 Traditional Mojo 186-187

ECONOMY COLLECTION

Contractor 42" 228-229
 Contractor 52" 226-227
 Contractor LED 214-215
 Contractor Plus 216-217
 Contractor Uni-Pack LED 212-213
 Contractor Uni-Pack with 3-Light 218-219
 Contractor Uni-Pack with Light 220-225
 Mesa 230
 Supra® 32" 210-211
 Supra® 44" 208-209
 Supra® 44" with Light 206-207
 Supra® 52" 202-205
 Supra® 52" with Light 200-201

Ultra-Max™ 198-199

ACCESSORY FAN BLADES 246-247

FAN CONTROL SYSTEMS

Compatibility Chart 234-235
 Fan Controls 232-233

FAN HANGING SYSTEMS

Accessories 238
 Downrods 236-238

GLASS SHADES 231

LIGHT KITS

Custom LED Light Kits 244-245
 Custom Light Kits 245
 Universal Light Kits 239-244

BULB REFERENCE 249

DIMENSIONS & SPECIFICATIONS 268-270

FAN STYLES 255-263

FINISH GUIDE 248-271

INDEX 250-254

Energy Efficiency



- DC motors are up to 67% more efficient than typical (AC Motor) ceiling fan motors
- Minka-Aire® DC motor fans use a maximum of 48 watts of electricity
- DC motors can move greater degree of fan blade pitches without adding significant energy consumption
- DC motors provide a wider range of fan speeds. All of Minka-Aire's DC motors offer 6 different fan speeds creating a more personalized comfort setting.



Look for this logo for fans that carry Minka-Aire's most energy efficient motor

DC MOTOR

Minka-Aire's DC Motor Features



DC MOTOR
AIRFLOW:
EXCELLENT

AC MOTOR
AIRFLOW:
GOOD

Benefits

- Limited Lifetime Motor Warranty
- Flatter laminations in the motor helps reduce motor buzz
- Minka-Aire® DC motors use the latest innovative technology and high quality materials
- DC motors are held to higher quality standards
- Currently Minka-Aire® uses 4 different DC motors, providing the flexibility to create amazing fan styles and designs.

Benefits of LED Lighting

1. Long Life

Longer lifetime is the number one benefit of LED lights. The diodes within our LEDs have an outstanding lifetime expectation of up to 30,000 hours.

2. Energy Efficiency

This is today's most efficient way of illumination and lighting, saving 80%-90% when compared to traditional lighting and conventional light bulbs.

3. Ecologically Friendly

LED lights are free of toxic chemicals. Most conventional fluorescent lighting bulbs contain a multitude of materials like e.g. mercury that are dangerous for the environment.

4. Durable Quality

LEDs are extremely durable and built with sturdy components that are highly rugged and can withstand the roughest conditions.

5. Zero UV Emissions

LED illumination produces little infrared light and close to no UV emissions, which attracts less insects.





6. All Minka-Aire® LED fans are dimmable as compared to CFLs which are not.



Room Size and Ceiling Height Recommendations


Room Size


These measurements are for general air flow requirements only. Decorating plans or aesthetic considerations should influence your fan choices beyond these room size specifications. For very large rooms, multiple fans is an option.

				
Blade Sweep	26"-42"	44"	52"-54"	60"-72"
Approximate Room Size	6' x 8' 40-60 sq. ft.	8' x 10' 70-90 sq. ft.	10' x 12' 100-150 sq. ft.	12' x 15' (Great Room) Over 160 sq. ft.

Ceiling Height

Be sure there is at least 7 feet of clearance under your ceiling fan blades. The standard 3½" and 6" downrods should work in most 8 foot ceiling installations. This will position the blades far enough from the ceiling to have enough "supply" air above the blades to provide good air movement. If greater floor to fan clearance is needed, some fans can use our low ceiling adapter (A180) without using any downrod. However, air movement is reduced using the low ceiling adapter. This chart shows recommended downrod lengths for various ceiling heights.





F838L-WH

White Finish
White Blades
with Etched Lens



F838L-SL

Silver Finish
Silver Blades
with Etched Lens
Shown with Optional K9838L-SL
LED Light Kit

Force

with LED Light

F838L-DK

Distressed Koa Finish
Distressed Koa Blades
with Etched Lens

A sleek, well proportioned, contemporary design featuring an integrated 15 watt LED* with a 60-inch sweep. The Force by Minka-Aire® will make a design statement in any décor.

Features:

- Variable Blade Pitch
- 3-Blades 60" Sweep
- DC 123 x 30mm Motor
- 3½" and 6" Downrods
- Special Hand Held Remote Control System Included - RC400
- Integrated LED Light
Uses 15W LED (Included)
3 Year Warranty
- 1,550 Lumens
- 3,000K
- CRI 80
- Custom LED Light Kit K9838L Available
(Sold Separately. Page(s): 245)

U.S. Patent(s): Pending

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
6,235	45.6	137



DC MOTOR

RC400

Full Function Hand Held Remote Control Include
For Details See Page(s): 232

Lifetime
WARRANTY

Remote
CONTROL
FULL FUNCTION

* LED (Light Emitting Diodes)

LED



F617L-GM

Gun Metal Finish
Gun Metal Blades
with Etched Opal Glass

LED



F617L-BN

Brushed Nickel Finish
Silver Blades
with Etched Opal Glass

Raptor

with LED Light



F617L-ORB/AB

Oil Rubbed Bronze / Antique Brass Finish
Toned Tobacco Blades
with Tinted Opal Glass

LED

This contemporary design is coupled with the energy saving advancements of DC motor technology and an integrated 17 watt LED light source. An option of three transitional finishes.

LED

Features:

- 14° Blade Pitch
- 5-Blades 60" Sweep
- 3½" and 6" Downrods
- DC 172 x 12mm Motor
- Special Hand Held Remote Control System Included - RC600
- Integrated LED Light
Uses 17W LED (Included)
3 Year Warranty
- 1,100 Lumens
- 3,000K
- CRI 80

U.S. Patent(s): Pending

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
7,039.28	32.57	216.12

Lifetime
WARRANTY

Remote
CONTROL
FULL FUNCTION



DC MOTOR

RC600

Full Function Hand Held Remote Control Included
For Details See Page(s): 232

Artemis™



F803-DK
 Distressed Koa Finish
 with Tinted Opal Glass

Features:

- Contoured Aerodynamic Vanes
- Variable Blade Pitch
- 3-Vanes 58" Sweep
- 3½" and 6" Downrods
- Full Function Wall Control System
- Integrated Halogen Light
 Uses 1-100W Mini-Can Halogen Bulb (Included)
- Cap for Non-Light Use (Included)

U.S. Patent(s): D535,011; D535,015; D535,387;
 D535,388; D536,083; 7,481,626

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
6,453	95	67.92



F803-LN
 Liquid Nickel Finish
 with Etched Opal Glass



WCS212
 Full Function Wall Control System Included
 For Details See Page(s): 233

Lifetime
 WARRANTY

WallControl
 FULL FUNCTION

GEORGE
KOVACS®

by

minkaAire®
A Minka Group® Co.



The distinct profile of the Artemis™ is captured by the Flying Vanes™ that incorporate the fan housing. A true design statement!

Winner of the 2005 Chicago Athenaeum: Museum of Architecture and Design's Good Design Award.



F803-MG

Mahogany Finish
with Etched Opal Glass

Artemis™



F803-RD

High Gloss Pure Red Finish
with Etched Opal Glass

Features:

- Contoured Aerodynamic Vanes
- Variable Blade Pitch
- 3-Vanes 58" Sweep
- 3½" and 6" Downrods
- Full Function Wall Control System
- Integrated Halogen Light
Uses 1-100W Mini-Can Halogen
Bulb (Included)
- Cap for Non-Light Use (Included)

U.S. Patent(s): D535,011; D535,015; D535,387;
D535,388; D536,083; 7,481,626

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
6,453	95	67.92



WCS212

Full Function Wall Control System Included
For Details See Page(s): 233

Lifetime
WARRANTY

WallControl
FULL FUNCTION



F803-CPBR

Copper Bronze Finish
with Tinted Opal Glass



F803-SL

Silver Finish
with Etched Opal Glass

Artemis™



F803-WH

High Gloss White Finish
with Etched Opal Glass



Features:

- Contoured Aerodynamic Vanes
- Variable Blade Pitch
- 3-Vanes 58" Sweep
- 3½" and 6" Downrods
- Full Function Wall Control System
- Integrated Halogen Light
Uses 1-100W Mini-Can Halogen
Bulb (Included)
- Cap for Non-Light Use (Included)

U.S. Patent(s): D535,011; D535,015; D535,387;
D535,388; D536,083; 7,481,626

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
6,453	95	67.92



WCS212

Full Function Wall Control System Included
For Details See Page(s): 233

F803-TL

Translucent Finish
with Etched Opal Glass

Lifetime
WARRANTY

WallControl
FULL FUNCTION

GEORGE
KOVACS®

by

minkaAire®
A Minka Group® Co.



F803-BK

High Gloss Black Finish
with Etched Opal Glass



F803-MP

Maple Finish
with Etched Opal Glass

Pancake



F738-SL

Silver Finish
Silver Blades



F738-ORB

Oil Rubbed Bronze Finish
Oil Rubbed Bronze Blades

Features:

- 12° Blade Pitch
- 4-Blades 52" Sweep
- **6" Internally Threaded Downrod**
- Max Ceiling Slope Angle 18°
- Full Function Hand Held Remote Control System

U.S. Patent(s): D750,215; D750,219
Additional U.S. Patent(s) Pending

Energy Information

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
5,405	63.9	84.58



RCS212

Full Function Hand Held Remote Control Included
For Details See Page(s): 232

Lifetime WARRANTY

Remote CONTROL
FULL FUNCTION



**F738-DK**

Distressed Koa Finish
Distressed Koa Blades

Our Pancake ceiling fan magically houses all the needed components of a high performance ceiling fan in a slim 3-inch deep body. Minimal, elegant and smooth, the profile is narrow, allowing for an unobtrusive, non-competing addition to any room.

**F738-WHF**

Flat White Finish
Flat White Blades

Ninety-Nine

with LED Light



F899L-BN/SL


Brushed Nickel Finish
Silver Blades
with Etched Opal Glass



Ninety-Nine

with LED Light

LED



Features:

- Variable Blade Pitch
- 9-Blades 99" Sweep
- DC 172 x 25mm Motor
- 3½" and 6" Downrods
- Special Hand Held Remote Control System Included - RC600
- Integrated LED Light
Uses 26W LED (Included)
3 Year Warranty
- 1,899 Lumens
- 2,700K
- CRI 81

U.S. Patent(s): Pending

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
13,350	45	295



DC MOTOR

LED

F899L-ORB

Oil Rubbed Bronze Finish
Toned Tobacco Blades
with Etched Opal Glass

RC600

Full Function Hand Held Remote Control Included
For Details See Page(s): 232

Lifetime
WARRANTY

Remote
CONTROL
FULL FUNCTION



Minka-Aire® introduces our Ninety-Nine fan, featuring a total of 99 inches in diameter! A refreshing transitional design featuring 9-blades, 26 watt LED* and a DC motor. Ideal for residential and commercial use. Includes a six speed hand held remote control and is reversible for winter and summer.

Ninety-Nine

with LED Light



Features:

- Variable Blade Pitch
- 9-Blades 99" Sweep
- DC 172 x 25mm Motor
- 3½" and 6" Downrods
- Special Hand Held Remote Control System Included - RC600
- Integrated LED Light
Uses 26W LED (Included)
3 Year Warranty
- 1,899 Lumens
- 2,700K
- CRI 81

U.S. Patent(s): Pending

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
13,350	45	295



DC MOTOR

LED

F899L-DK

Distressed Koa Finish
Distressed Koa Blades
with Etched Opal Glass

RC600

Full Function Hand Held Remote Control Included
For Details See Page(s): 232

Lifetime
WARRANTY

Remote
CONTROL
FULL FUNCTION

LED

Minka-Aire® introduces our Ninety-Nine fan, featuring a total of 99 inches in diameter! A refreshing transitional design featuring 9-blades, 26 watt LED* and a DC motor. Ideal for residential and commercial use. Includes a six speed hand held remote control and is reversible for winter and summer.



LED

F899L-BN/SL

Brushed Nickel Finish
Silver Blades
with Etched Opal Glass

* LED (Light Emitting Diodes)




F887-72-BN 72"
F887-80-BN 80"
F887-88-BN 88" (Shown)
F887-96-BN 96"

□ Brushed Nickel Finish
Silver Blades

This industrial size fan lends itself to almost any setting. Xtreme's clean, sleek, contemporary design with a DC motor and a choice of sizes makes it perfect for large areas.

Xtreme



Features:

- 4° Blade Pitch
- 9-Blades 72", 80", 88" or 96" Sweep
- DC 165 x 25mm Motor
- 3½" and 6" Downrods
- Aluminum Blades
- Install with Blades at least 10' above the Floor
- Special Hand Held Remote Control System Included - RC400

Energy Information for 72"
(Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
10,203	29	352

Energy Information for 80"
(Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
10,298	30	343.3

Energy Information for 88"
(Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
12,209	31	393.9

Energy Information for 96"
(Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
13,080	30.5	428.9



RC400

Full Function Hand Held Remote Control Included
For Details See Page(s): 232





F887-72-ORB 72"

F887-80-ORB 80"

F887-88-ORB 88" (Shown)

F887-96-ORB 96"




Oil Rubbed Bronze Finish

Oil Rubbed Bronze Blades

This industrial size fan lends itself to almost any setting. Xtreme's clean, sleek, contemporary design with a DC motor and a choice of sizes makes it perfect for large areas.

Xtreme



Features:

- 4° Blade Pitch
- 9-Blades 72", 80", 88" or 96" Sweep
- DC 165 x 25mm Motor
- 3½" and 6" Downrods
- Aluminum Blades
- Install with Blades at least 10' above the Floor
- Special Hand Held Remote Control System Included - RC400

Energy Information for 72"
(Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
10,203	29	352

Energy Information for 80"
(Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
10,298	30	343.3

Energy Information for 88"
(Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
12,209	31	393.9

Energy Information for 96"
(Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
13,080	30.5	428.9



RC400

Full Function Hand Held Remote Control Included
For Details See Page(s): 232



Slipstream XXL



Features:

- 14° Blade Pitch
- 8-Concave Blades 84" Sweep
- DC 165 x 25mm Motor
- Galvanized Steel 3½" and 6" Downrods
- Stainless Steel Hardware and All Weather Blades
- Special Hand Held Remote Control System Included - RC400
- Integrated Light Uses 1-26W GU24 Non-Dimmable CFL (Included)
- Cap for Non-Light Use (Included)
- Indoor/Outdoor Use UL Listed for Wet Locations

F889-BNW

Brushed Nickel Wet Finish
Silver Blades
with Etched Opal Glass



DC MOTOR

RC400

Full Function Hand Held Remote Control Included
For Details See Page(s): 232

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
11,022	26.8	411.27

Lifetime WARRANTY

Remote CONTROL FULL FUNCTION



UL LISTED For Wet Location





Shown with Cap for Non-Light Use

Slipstream XXL is the second generation of our uniquely designed 8 blade fan. Slipstream XXL has grown to 84 inches, making this a power house of air flow and designed with enough presence to be used in both residential and commercial environments. In addition, it has a UL listing for both indoor and outdoor spaces.

Slipstream XXL



F889-ORB

Oil Rubbed Bronze Finish
Oil Rubbed Bronze Blades
with Tinted Opal Glass
Shown with Cap for Non-Light Use

Features:

- 14° Blade Pitch
- 8-Concave Blades 84" Sweep
- DC 165 x 25mm Motor
- Galvanized Steel
3½" and 6" Downrods
- Stainless Steel Hardware and
All Weather Blades
- Special Hand Held Remote Control
System Included - RC400
- Integrated Light
Uses 1-26W GU24 Non-Dimmable
CFL (Included)
- Cap for Non-Light Use (Included)
- Indoor/Outdoor Use
UL Listed for Wet Locations



RC400

Full Function Hand Held Remote Control Included
For Details See Page(s): 232

DC MOTOR

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
11,022	26.8	411.27

Lifetime
WARRANTY

Remote
CONTROL
FULL FUNCTION



UL
LISTED
For Wet Location



Slipstream XXL is the second generation of our uniquely designed 8 blade fan. Slipstream XXL has grown to 84 inches, making this a power house of air flow and designed with enough presence to be used in both residential and commercial environments. In addition, it has a UL listing for both indoor and outdoor spaces.

**F889-SI**

Smoked Iron Finish
Smoked Iron Blades
with Etched Opal Glass

Slipstream



F888-BNW

Brushed Nickel Wet Finish
Silver Blades
with Etched Opal Glass

Features:

- 14° Blade Pitch
- 8-Concave Blades 65" Sweep
- DC 165 x 25mm Motor
- Galvanized Steel 3½" and 6" Downrods
- Stainless Steel Hardware and All Weather Blades
- Special Hand Held Remote Control System Included - RC400
- Integrated Light Uses 1-18W GU24 Non-Dimmable Squat CFL (Included)
- Cap for Non-Light Use (Included)
- Indoor/Outdoor Use UL Listed for Wet Locations



RC400

Full Function Hand Held Remote Control Included
For Details See Page(s): 232

DC MOTOR

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
8,778	27.6	318.04

Sleek industrial styling destines this 8-bladed wonder to make a cool statement in any indoor or outdoor setting.

U.S. Patent(s): D715,917



For Wet Location





F888-WHF

Flat White Finish
Flat White Blades
with Etched Opal Glass



F888-DK

Distressed Koa Finish
Distressed Koa Blades
with Tinted Opal Glass



F888-ORB

Oil Rubbed Bronze Finish
Oil Rubbed Bronze Blades
with Tinted Opal Glass

Shown with Cap for Non-Light Use

GEORGE
KOVACS®

by

minkaAire®
A Minka Group® Co.

F905-SL

Silver Finish
with Etched Opal Glass

Features:

- Variable Blade Pitch
- 5-Blades 62" Sweep
- DC 172 x 25mm Motor
- 3½" and 6" Downrods
- Special Hand Held Remote Control System Included - RC600
- Integrated Halogen Light
Uses 1-100W Mini-Can Halogen Bulb (Included)
- Cap for Non-Light Use (Included)

U.S. Patent(s): D721,430

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
8,289	41.48	199.83



RC600

Full Function Hand Held Remote Control Included
For Details See Page(s): 232

The big brother of our original Artemis™, the distinct profile of the Artemis™ XL5 is captured by the five Flying Vanes™ that encase the fan housing - creating a true design statement!

DC MOTOR

Lifetime
WARRANTY


Remote
CONTROL
FULL FUNCTION

Artemis™ XL5



F905-DK

Distressed Koa Finish
with Tinted Opal Glass



F905-WH

White Finish
with Etched Opal Glass

Shown with Cap for Non-Light Use

Aviation

F853-BN/DK

Brushed Nickel Finish
Distressed Koa Blades

Features:

- Variable Blade Pitch
- 3-Blades 60" Sweep
- DC 120 x 25mm Motor
- 3½" and 6" Downrods
- Special Hand Held Remote Control System Included - RC500

U.S. Patent(s): D721,429; D721,800; D726,298

Energy Information

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
6,604	25.92	254.80

Lifetime
WARRANTY

Remote
CONTROL
FULL FUNCTION



RC500

Full Function Hand Held Remote Control Included
For Details See Page(s): 232


DC MOTOR



GEORGE
KOVACS®

by

minkaAire®
A Minka Group® Co.



Inspired by the classic form of vintage aircraft propellers, our Aviation fan has an updated appeal that addresses a new audience with sleek, elegant lines and a combination of finish techniques that work for all of today's trends.

F853-RW

Rosewood Finish
Rosewood Blades

Aviation

F853-WH

White Finish
White Blades

Features:

- Variable Blade Pitch
- 3-Blades 60" Sweep
- DC 120 x 25mm Motor
- 3½" and 6" Downrods
- Special Hand Held Remote Control System Included - RC500

U.S. Patent(s): D721,429; D721,800; D726,298

Energy Information

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
6,604	25.92	254.80

Lifetime
WARRANTY

Remote
CONTROL
FULL FUNCTION



DC MOTOR

RC500

Full Function Hand Held Remote Control Included
For Details See Page(s): 232





□ **F853-BN/MM**

Brushed Nickel Finish
Medium Maple Blades



□ **F853-BN/SL**

Brushed Nickel Finish
Silver Blades

Spectre

with LED Light

LED



F726-BN/SL

Brushed Nickel Finish
Silver Blades
with Clear Lens

Features:

- 14° Blade Pitch
- 4-Blades 60" Sweep
- DC 188 x 10MM Motor
- 3½" and 6" Downrod
- Special Hand Held Remote Control System Included - RC400
- Integrated LED Light
Uses 17W LED (Included)
3 Year Warranty
- 1,100 Lumens
- 3,000K
- CRI 80

U.S. Patent(s): Pending

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
7,230	31.8	227.35



DC MOTOR

LED

Versatile, industrial styling and creative details are the key to Spectre. The distinctive blade irons hug the fan body, providing a unique look compatible with contemporary environments.

Lifetime
WARRANTY

Remote
CONTROL
FULL FUNCTION

RC400

Full Function Hand Held Remote Control Included
For Details See Page(s): 232

LED



F726-WHF/BN

Flat White / Brushed Nickel Finish
Flat White Blades
with Clear Lens



F726-BN/ORG

Brushed Nickel / Orange Finish
Orange Blades
with Clear Lens

Spectre

with LED Light

LED

LED



F726-ORB/AB

Oil Rubbed Bronze / Antique Brass Finish
Toned Tobacco Blades
with Clear Lens

Features:

- 14° Blade Pitch
- 4-Blades 60" Sweep
- DC 188 x 10mm Motor
- 3½" and 6" Downrod
- Special Hand Held Remote Control System Included - RC400
- Integrated LED Light
Uses 17W LED (Included)
3 Year Warranty
- 1,100 Lumens
- 3,000K
- CRI 80

U.S. Patent(s): Pending

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
7,230	31.8	227.35



LED

F726-WHF/BN

Flat White / Brushed Nickel Finish
Flat White Blades
with Clear Lens



DC MOTOR

RC400

Full Function Hand Held Remote Control Included
For Details See Page(s): 232

Lifetime
WARRANTY

Remote
CONTROL
FULL FUNCTION

LED

F726-ORB/BN

Oil Rubbed Bronze / Brushed Nickel Finish
Oil Rubbed Bronze Blades
with Clear Lens

Versatile, industrial styling and creative details are the key to Spectre. The distinctive blade irons hug the fan body, providing a unique look compatible with contemporary environments.

LED

LED

Simple



F787-ORB

Oil Rubbed Bronze Finish
Medium Maple Blades

Features:

- 14° Blade Pitch
- 3-Blades 52" Sweep
- DC 123 x 30mm Motor
- 3½" and 6" Downrods
- Special Hand Held Remote Control System Included - RC400
- Custom 15W LED Light Kit K9787L Available (Sold Separately. Page(s): 244)
- Indoor/Outdoor Use
ETL Listed for Wet Locations

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
7,051	33.1	213

So simple! We gave this wonderful design a name that best denotes it's spirit! Incredibly delicate and nearly invisible. This design best displays the advancement in technology with indoor/outdoor use, DC motor, optional LED* light kit and a hand held remote.

Lifetime
WARRANTY

Remote
CONTROL
FULL FUNCTION



DC MOTOR


RC400

Full Function Hand Held Remote Control Included
For Details See Page(s): 232



Intertek
For Wet Location





F787-SL

□ Silver Finish
Silver Blades
Shown with Optional K9787L-SL
LED Light Kit



F787-WHF

□ Flat White Finish
Flat White Blades
Shown with Optional K9787L-WHF
LED Light Kit

Roto



F524-ABD

Brushed Aluminum Finish
Silver Blades

Features:

- 22° Blade Pitch
- 3-Blades 52" Sweep
- 3½" and 6" Downrods
- Aluminum Construction
- Converts to Electronic Control System

U.S. Patent(s): D750,221
Additional U.S. Patent(s) Pending

Energy Information

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
5,816	51.5	113

Roto features a sleek and contemporary design with a classic industrial look. Well edited and an impeccably executed design features a slight "fold" construction along the length of the blades to increase the flow of air. A perfect marriage of form and function.

Lifetime
WARRANTY


WallControl



WC105-WH

Wall Control System Included
For Details See Page(s): 233

See Page 146 for Roto XL Family



F524-WHF
Flat White Finish
Flat White Blades



F524-DK
Distressed Koa Finish
Distressed Koa Blades



F524-ORB
Oil Rubbed Bronze Finish
Oil Rubbed Bronze Blades

Sabot

with LED Light

LED

LED



F745-DK

Distressed Koa Finish
Reversible Medium Maple / Dark Walnut Blades
with White Lens
(Shown with Dark Walnut Blades)

Features:

- 12° Blade Pitch
- 5-Blades 52" Sweep
- DC 172 x 12mm Motor
- 3½" and 6" Downrods
- Special Hand Held Remote Control System - RC600
- Integrated LED Light
Uses 17W LED (Included)
3 Year Warranty
- 1,100 Lumens
- 3,000K
- CRI 80

U.S. Patent(s): Pending

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
5,779	33	175.12



DC MOTOR

RC600

Full Function Hand Held Remote Control Included
For Details See Page(s): 232

LED

Lifetime WARRANTY

Remote CONTROL FULL FUNCTION

LED



LED

□ **F745-BN**

Brushed Nickel Finish
Silver Blades
with White Lens



□ **F745-ORB**

Oil Rubbed Bronze Finish
Reversible Medium Maple / Dark Walnut Blades
with White Lens
(Shown with Medium Maple Blades)


LED

Symbio

with LED Light

LED Light
LED Light
LED Light

LED



F828-BN

Brushed Nickel Finish
Silver Blades
with Etched Glass



F828-ORB

Oil Rubbed Bronze Finish
Medium Maple Blades
with Tea Stain Glass

LED



F828-WHF

Flat White Finish
Flat White Blades
with Etched Glass

LED

F828-BN/DW

Brushed Nickel Finish
Dark Walnut Blades
with Etched Glass

This clean contemporary powerhouse delivers the air flow of larger fans using DC motor technology to keep energy consumption to a minimum while the integrated DC LED* light provides energy efficient illumination.

Features:

- 15° Blade Pitch
- 5-Blades 56" Sweep
- DC 125 x 30mm Motor
- 3½" and 6" Downrod
- Special Hand Held Remote Control System Included - RC400
- Integrated LED Light Uses 16W DC LED (Included) 3 Year Warranty
- 1,352 Lumens
- 2,700K
- CRI 80

U.S. Patent(s): Pending

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
6,363	31.6	201.36



Shown with Optional White Downrod

F828-BN/WH

Brushed Nickel Finish
White Blades
with Etched Glass

Lifetime
WARRANTY

Remote
CONTROL
FULL FUNCTION



RC400

Full Function Hand Held Remote Control Included
For Details See Page(s): 232

* LED (Light Emitting Diodes)

LED

F753L-BNW

Brushed Nickel Wet Finish
Silver Blades
with Etched Opal Glass

Minka-Aire's "everywhere" fan with a unique contemporary twist that is suitable for all indoor or outdoor environments. The Java LED features an integrated 17 watt LED* light.

LED

F753L-WHF

Flat White Finish
Flat White Blades
with Etched Opal Glass

Java LED

with LED Light

LED

F753L-KA

Kocoa Finish
Kocoa Blades
with Etched Opal Glass

Features:

- 14° Blade Pitch
- 3-Blades 54" Sweep
- 3½" and 6" Downrod
- Hand Held Remote Control System
- Integrated LED Light
Uses 17W LED (Included)
3 Year Warranty
- 1,350 Lumens
- 3,000K
- CRI 80
- Indoor/Outdoor Use - UL Listed for Wet Locations

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
5,682	47	121

F753L-PN

Polished Nickel Finish
Silver Blades
with Etched Opal Glass
(Finish For Indoor Use Only)



RCS213

Hand Held Remote Control Included
For Details See Page(s): 232

Lifetime
WARRANTY

Remote
CONTROL



LISTED
For Wet Location



See Page 52 for Java Family



F753-PN

Polished Nickel Finish
Silver Blades
(Finish For Indoor Use Only)

Minka-Aire's "everywhere" fan with a unique contemporary twist that is suitable for all environments.



F753-WHF

Flat White Finish
Flat White Blades

Aluma



F521-ABD

Brushed Aluminum Finish
Silver Blades
with Etched Opal Glass

Features:

- 12° Blade Pitch
- 4-Blades 52" Sweep
- 3½" and 6" Downrods
- WC106 4-Speed Full Range Dimmer
- Converts to Electronic Control System
- All Aluminum Construction
- Integrated Halogen Light
Uses 1-100W Mini-Can Halogen Bulb (Included)
- Cap for Non-Light Use (Included)

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
5,471	66.6	82.15



WC106-WH

Wall Control System Included
For Details See Page(s): 233



See Page 162 for Aluma Wet Family

Lifetime
WARRANTY

WallControl

The Aluma is minimal in form with a youthful soft contemporary twist that makes it a fan with universal appeal.



□ **F521-ORB**

Oil Rubbed Bronze Finish
Oil Rubbed Bronze Blades
with Tinted Opal Glass

□ **F521-WHF**

Flat White Finish
Flat White Blades
with Etched Opal Glass
Shown with Cap for Non-Light Use

Wing

F823-DK

Distressed Koa Finish

Winner of the 2010 Chicago
Athenaeum: Museum of Architecture
and Design's Good Design Award.

Features:

- Variable Blade Pitch
- 1-Wing 52" Sweep
- DC 125 x 30mm Motor
- 6" Downrod
- Special Hand Held Remote Control System Included - RC400

U.S. Patent(s): D678,977; 9,004,863
Additional U.S. Patent(s) Pending

Energy Information

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
5,974	30.2	197.81

Lifetime
WARRANTY

Remote
CONTROL
FULL FUNCTION



DC MOTOR

RC400

Full Function Hand Held Remote Control Included
For Details See Page(s): 232



A unique 52" single wing fan that transcends all conventional designs.



F823-SL

□ Silver Finish



F823-WH

□ High Gloss White Finish

Light Wave

with LED Light

LED

LED



F844-DK

Distressed Koa Finish
Distressed Koa Blades
with Etched Lens

Features:

- Variable Blade Pitch
- 3-Blades 52" Sweep
- 4½" and 6" Downrods
- Hand Held Remote Control System
- Integrated Light
Uses 17W Dimmable LED
(Included) 3 Year Warranty
- 1,100 Lumens
- 3,000K
- CRI 80
- Replacement LED Assembly
(Part #6F844LK01)

U.S. Patent(s): D750,213
Additional U.S. Patent(s) Pending

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
5,024	65.3	76.94



RCS213

Hand Held Remote Control Included
For Details See Page(s): 232

Light Wave is the next generation of our highly successful, ground-breaking Wave fan. Its energy-efficient LED* light source integrates light without compromising design.

LED

Lifetime WARRANTY
Remote CONTROL

LED



F844-WH


White Finish
White Blades
with Etched Lens



F844-SL

Silver Finish
Silver Blades
with Etched Lens

Wave



F843-SL

Silver Finish

Features:

- Variable Blade Pitch
- 3-Blades 52" Sweep
- 4½" and 6" Downrods
- Hand Held Remote Control System

U.S. Patent(s): D715,419; D715,421

Energy Information

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
6,580	66.4	99

A truly unique design that draws inspiration from the ocean's graceful and tubular wave formations.

Lifetime
WARRANTY

Remote
CONTROL



RCS213

Hand Held Remote Control Included
For Details See Page(s): 232





F843-DK
Distressed Koa Finish



F843-WH
White Finish

Kewl



□ **F833-RD**
Red Finish

Features:

- 22° Blade Pitch
- 3-Blades 52" Sweep
- 3½" and 6" Downrods
- Converts to Electronic Control System

U.S. Patent(s): D715,418; D726,299

Special Note:


- Custom Finish Orders Accepted
 - 200 Piece Minimum Order Per Finish
 - 90 Day Lead Time

Energy Information

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
6,304	55	114.62



□ **WC105-WH**
Wall Control System Included
For Details See Page(s): 233



□ **F833-WH**
White Finish

Lifetime
WARRANTY

WallControl





F833-SL
Silver Finish



A traditional design, now morphed to a contemporary style, creating a synergistic blend that's perfect for numerous settings.



F833-BK
Black Finish



F531-L-BN

Brushed Nickel Finish
Birdseye Maple Blades
with White Opal Glass



F531-L-WH

White Finish
High Gloss White Blades
with White Opal Glass

Flyte®

Winner of the 2001 Chicago
Athenaeum: Museum of Architecture
and Design's Good Design Award

F531-L-BN/MG

Brushed Nickel Finish
Mahogany Blades
with White Opal Glass
Mahogany Downlink™

Shown with Cap for Non-Light Use

The essence of simplicity and elegance, the Flyte® fan's combination of integrated halogen light and distinctive hanging system gives this contemporary design a compelling and sophisticated presence.

Features:

- 14° Blade Pitch
- 3-Blades 56" Sweep
- Includes 9" Downlink™ Hanging System with ½" I.D. Downrod
- Wall Control System
- Integrated Halogen Light
Uses 1-100W Mini-Can Halogen Bulb (Included)
- Suitable for Installation on Vaulted Ceilings up to 21°
- Capable of using 3½" Downrod for Low Ceiling Application (Part #DR235-44 and #DR235-BN)
- Cap for Non-Light Use (Included)

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
5,703	67	85.12



WCS213

Wall Control System Included
For Details See Page(s): 233

Lifetime
WARRANTY **WallControl**

Accessory Blades Available. See Page(s): 246

Additional Downlink™ Options Available
See Page(s): 238

Winner of the 1998 Chicago
Athenaeum: Museum of Architecture
and Design's Good Design Award

F529-L-ORB

- Oil Rubbed Bronze Finish
Medium Maple Blades
with Tinted Opal Glass

F528-L-BS/CH

- Brushed Steel / Chrome Finish
Birdseye Maple Blades

San Francisco®



F529-L-BS/CH

Brushed Steel / Chrome Finish
Birdseye Maple Blades
with Frosted Opal Glass

The bold, clean lines and simplicity of the San Francisco® fan make it a timeless architectural design element, suited for any interior.

Features:

- 13° Blade Pitch
- 3-Blades 56" Sweep
- Includes 12" Pre-Wired Downbridge™ Hanging System
- Wall Control System
- Integrated Halogen Light
Uses 1-75W JDR Intermediate Base Bulb (Included)
- Suitable for Installation on Vaulted Ceilings up to 30°

U.S. Patent(s): 5,951,253; 6,158,964; 6,171,060; 6,250,885

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
5,780	77	75.02



WCS213

Wall Control System Included
For Details See Page(s): 233

Lifetime
WARRANTY **WallControl**

Accessory Blades Available. See Page(s): 246

Additional Downbridge™ Options Available.
See Page(s): 238

Gilera

F733-BK/RW

Black / Rosewood Finish
Rosewood Blades

Features:

- 14° Blade Pitch
- 3-Blades 62" Sweep
- 3½" and 6" Downrods
- Full Function Wall Control System

U.S. Patent(s): D728,775; D747,452

Energy Information

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
6,431	102.8	62.55



WCS212

Full Function Wall Control System Included
For Details See Page(s): 233

Lifetime
WARRANTY

WallControl
FULL FUNCTION

Vintage Italian racing motorcycles served as the design vision for the Gilera ceiling fan. With its 62-inch sweep, Gilera is specially designed for use in rooms with greater ceiling

heights. Highly detailed and dramatically proportioned, Gilera is destined to become an heirloom of the future.

F733-SL

□ Silver Finish
Silver Blades

Gilera



F733-BS/BN

Brushed Steel / Brushed Nickel Finish
Medium Maple Blades



F733-PN

Polished Nickel Finish
Silver Blades

Features:

- 14° Blade Pitch
- 3-Blades 62" Sweep
- 3½" and 6" Downrods
- Full Function Wall Control System

U.S. Patent(s): D728,775; D747,452

Energy Information

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
6,431	102.8	62.55



WCS212

Full Function Wall Control System Included
For Details See Page(s): 233

Lifetime
WARRANTY

WallControl
FULL FUNCTION



F733-WH
White Finish
White Blades



Moda



F737-BN

Brushed Nickel Finish
Silver Blades
with Etched White Glass



F737-WH

White Finish
White Blades
with Etched White Glass

Features:

- 20° Blade Pitch
- 3-Blades 60" Sweep
- DC 188 x 14mm Motor
- 3½" and 6" Downrods
- Integrated Uplight
Use 10-15W Candelabra Bulbs
(Included)
- Special Hand Held Remote Control
System Included - RC500

U.S. Patent(s): D750,214; D750,220

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
8,421	27.9	302



DC MOTOR

RC500

Full Function Hand Held Remote Control Included
For Details See Page(s): 232

Lifetime
WARRANTY

Remote
CONTROL
FULL FUNCTION

Versatile, transitional styling and creative details are the key to Moda. Injection molded blades uniquely hug close to the hub. Moda incorporates an etched glass shade that directs light up toward the ceiling, producing a glowing up-light effect.



F737-ORB

Oil Rubbed Bronze Finish
Dark Maple Blades
with Tea Stained Glass



F516-ORB 44"

F517-ORB 52"

Oil Rubbed Bronze Finish
Taupe Blades
with White Opal Glass



F516-WH 44"

F517-WH 52"

White Finish
White Blades
with White Opal Glass

Concept™ I

F516-PN 44"
F517-PN 52"

Polished Nickel Finish
Silver Blades
with White Opal Glass



Features:

- 14° Blade Pitch
- 3-Concave Blades 44" or 52" Sweep
- 3½" and 6" Downrods
- Full Function Hand Held Remote Control System
- Integrated Halogen Light
Uses 1-100W Mini-Can Halogen Bulb (Included)
- Cap for Non-Light Use (Included)

U.S. Patent(s): D475,782; D476,408; D478,654;
D478,980; 7,008,192

F516 Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
3,987	46	86.68

F517 Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
6,028	61	98.82

F516-BN 44"
F517-BN 52"

Brushed Nickel Finish
Silver Blades
with White Opal Glass

Shown with Cap for Non-Light Use



RCS212

Full Function Hand Held Remote Control Included
For Details See Page(s): 232

See Page 150 for Concept™ I Wet Family

Lifetime
WARRANTY

Remote
CONTROL
FULL FUNCTION

Accessory Blades Available. See Page(s): 246

Concept™ II

52"

F519-BN

Brushed Nickel Finish
Silver Blades
with White Opal Glass



F519-ORB

Oil Rubbed Bronze Finish
Taupe Blades
with White Opal Glass



F519-PN

Polished Nickel Finish
Silver Blades
with White Opal Glass





F519-WH

White Finish
White Blades
with White Opal Glass

As the name implies, "a taste of things to come," simple in style, yet ingenious by design, the Concept™ II requires 75% less time and labor to assemble than conventional ceiling fans.

Features:

- 14° Blade Pitch
- 3-Concave Blades 52" Sweep
- Flush Mount - Ideal for Low Ceilings
Total Hanging Depth 11½" with or without Light
- Full Function Hand Held Remote Control System
- Integrated Halogen Light
Uses 1-100W Mini-Can Halogen Bulb (Included)
- Cap for Non-Light Use (Included)

U.S. Patent(s): D478,654; D478,974; D478,980; 7,008,192

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
5,710	55	103.82



F519-MG

Mahogany Finish
Mahogany Blades
with White Opal Glass

Lifetime
WARRANTY

Remote
CONTROL
FULL FUNCTION



RCS212

Full Function Hand Held Remote Control Included
For Details See Page(s): 232

Accessory Blades Available. See Page(s): 246

See Page 152 for Concept™ II Wet Family

Concept™ II

44"



F518-WH

White Finish
White Blades
with White Opal Glass

As the name implies, "a taste of things to come," simple in style, yet ingenious by design, the Concept™ II requires 75% less time and labor to assemble than conventional ceiling fans.



F518-BN

Brushed Nickel Finish
Silver Blades
with White Opal Glass



F518-ORB

Oil Rubbed Bronze Finish
Taupe Blades
with White Opal Glass

Features:

- 14° Blade Pitch
- 3-Concave Blades 44" Sweep
- Flush Mount - Ideal for Low Ceilings
Total Hanging Depth 11½" with or without Light
- Full Function Hand Held Remote Control System
- Integrated Halogen Light
Uses 1-100W Mini-Can Halogen Bulb (Included)
- Cap for Non-Light Use (Included)

U.S. Patent(s): D478,654; D478,974; D478,980; 7,008,192

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
4,071	43.7	93.16

Lifetime
WARRANTY

Remote
CONTROL
FULL FUNCTION



RGS212

Full Function Hand Held Remote Control Included
For Details See Page(s): 232

Accessory Blades Available. See Page(s): 246



F518-PN

Polished Nickel Finish
Silver Blades
with White Opal Glass

Shown with Cap for Non-Light Use

Traditional Concept™ 52"



F594-ORB

Oil Rubbed Bronze Finish
Medium Maple Blades
with Tinted Opal Glass

Features:

- 14° Blade Pitch
- 3-Blades 52" Sweep
- Flush Mount - Ideal for Low Ceilings
Total Hanging Depth 10¾"
- Full Function Wall Control System
- Integrated Halogen Light
Uses 1-100W Mini-Can Halogen Bulb (Included)
- Indoor/Outdoor Use
UL Listed for Wet Locations
- Cap for Non-Light Use (Included)

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
6,565	60.5	108.58

A variation on our best selling contemporary Concept™ II fan, this fan provides the same superb styling for your more traditional indoor and outdoor settings.

Lifetime
WARRANTY

WallControl
FULL FUNCTION



WCS212

Full Function Wall Control System Included
For Details See Page(s): 233



LISTED
For Wet Location





F594-PW

Pewter Finish
Dark Maple Blades
with Opal Glass



F594-WH

White Finish
White Blades
with Opal Glass

Traditional Concept™ 44"



F593-PW

Pewter Finish
Dark Maple Blades
with Opal Glass

Features:

- 14° Blade Pitch
- 3-Blades 44" Sweep
- Flush Mount - Ideal for Low Ceilings
Total Hanging Depth 10¾"
- Full Function Wall Control System
- Integrated Halogen Light
Uses 1-100W Mini-Can Halogen Bulb (Included)
- Indoor/Outdoor Use
UL Listed for Wet Locations
- Cap for Non-Light Use (Included)

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
4,940	49	100

Lifetime
WARRANTY

WallControl
FULL FUNCTION

UL
LISTED
For Wet Location



WCS212

Full Function Wall Control System Included
For Details See Page(s): 233

A variation on our best selling contemporary Concept™ II fan, this fan provides the same superb styling for your more traditional indoor and outdoor settings.



F593-ORB

Oil Rubbed Bronze Finish
Medium Maple Blades
with Tinted Opal Glass



F593-WH

White Finish
White Blades
with Opal Glass

Shown with Cap for Non-Light Use

Uchiwa



F824-ORB/TB

Oil Rubbed Bronze / Toned Brass Finish
Oil Rubbed Bronze Blades
with Tinted Opal Glass

うちわ

Harmoniously marked by characteristics and finishes of the present period, the Uchiwa is a functional art piece.

Features:

- 16° Blade Pitch
- 3-Blades 56" Sweep
- 3½" and 6" Downrods
- Full Function Wall Control System
- Integrated Halogen Light
Uses 1-75W Mini-Can Halogen Bulb (Included)

U.S. Patent(s): D618,786; D618,787; D620,586

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
4,574	58	78.86



WCS212

Full Function Wall Control System Included
For Details See Page(s): 233

Lifetime WARRANTY

WallControl FULL FUNCTION



F824-BK/CH

Black / Chrome Finish
Silver Blades
with Etched Opal Glass



F824-WH

White Finish
White Blades
with Etched Opal Glass

by



F596-BN

Brushed Nickel Finish
Silver Blades
with Etched Glass

Winner of the 2003 Chicago
Athenaeum: Museum of Architecture
and Design's Good Design Award

Features:

- 14° Blade Pitch
- 3-Blades 54" Sweep and 3-Blades 25" Sweep
- 4" and 6" Downrods
- Full Function Wall Control System
- Integrated Halogen Light
Uses 1-50W MR16 120V 2-Pin
Halogen Bulb (Included)
- Cap for Non-Light Use (Included)

U.S. Patent(s): D510,621; D513,316; D514,689;
D524,433; D549,816

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
5,087	49	103.81



WCS212

Full Function Wall Control System Included
For Details See Page(s): 233



F596-BN

Brushed Nickel Finish
Shown with Optional FB196-MG Blades

Lifetime
WARRANTY

WallControl
FULL FUNCTION

Accessory Blades Available. See Page(s): 246

Cirque™



F596-PN/TL

Polished Nickel Finish
Translucent Blades
with Etched Glass



F596-BN

Brushed Nickel Finish
Shown with Optional FB196-RYB Blades

Acero™



Winner of the 1999 Chicago Athenaeum: Museum of Architecture and Design's Good Design Award

F601-BS/MG

Brushed Steel / Mahogany Finish
Mahogany Blades
with Opal Frosted Glass

Features:

- 14° Blade Pitch
- 3-Concave Blades 52" Sweep
- 3½" and 6" Downrods
- Unique Wire Form Design
- Full Function Wall Control System
- Integrated Halogen Light
Uses 1-100W Mini-Can Halogen Bulb (Included)
- Cap for Non-Light Use (Included)

U.S. Patent(s): 6,354,801; 6,517,316


Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
6,465	69	93.69



WCS212

Full Function Wall Control System Included
For Details See Page(s): 233



F601-BS/BN

Brushed Steel / Brushed Nickel Finish
Silver Blades
with Opal Frosted Glass

Shown with Cap for Non-Light Use

Lifetime
WARRANTY

WallControl
FULL FUNCTION



F601-PN

- Polished Nickel Finish
- Silver Blades
- with Opal Frosted Glass

An evolution of form and function merging today's technology with contemporary styling, this fan comes with an integrated light.



F601-ORB

- Oil Rubbed Bronze Finish
- Aaron Mahogany Blades
- with Opal Frosted Glass



F603-ORB

Oil Rubbed Bronze Finish
Tobacco Blades
with Satin White Opal Glass



F603-WH

White Finish
White Blades
with Satin White Opal Glass

Como™



F603-BN

Brushed Nickel Finish
Silver Blades
with Satin White Opal Glas

Como™ is a harmonious, versatile design with clean, contemporary lines highlighted with subtle chrome, bronze and brushed nickel accents.

Features:

- 14° Blade Pitch
- 5-Blades 54" Sweep
- 3½" and 6" Downrods
- Full Function Wall Control System
- Integrated Halogen Light
Uses 2-75W Mini-Can Halogen Bulbs (Included)

U.S. Patent(s): D476,728

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
6,761	92	73.29



WCS212

Full Function Wall Control System Included
For Details See Page(s): 233

Lifetime
WARRANTY

WallControl
FULL FUNCTION



F514-ORB

- Oil Rubbed Bronze Finish
- Medium Maple Blades
- with Tinted Opal Glass



F514-BN

- Brushed Nickel Finish
- Silver Blades
- with White Frosted Glass
- Shown with Cap for Non-Light Use

Zen



F514-WH

White Finish
White Blades
with White Frosted Glass

A clean modern profile is accentuated in three finish options.

Features:

- 14° Blade Pitch
- 4-Blades 52" Sweep
- 3½" and 6" Downrods
- Full Function Hand Held Remote Control System
- Integrated Light Kit
Uses 2-13W Non-Dimmable GU24 CFL Bulbs (Included)
- Cap for Non-Light Use (Included)

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
6,148	71	86.05



RCS212

Full Function Hand Held Remote Control Included
For Details See Page(s): 232

Lifetime
WARRANTY

Remote
CONTROL
FULL FUNCTION



Airus™



F598-ORB

Oil Rubbed Bronze Finish
Medium Maple Blades
with Excavation Glass

Features:

- 14° Blade Pitch
- 5-Blades 54" Sweep
- 3½" and 6" Downrods
- Full Function Wall Control System
Independent Up/Downlight
- Integrated Halogen Uplight
Uses 2-50W Mini-Can Halogen
Bulbs (Included)
- Integrated Halogen Downlight
Uses 2-50W Mini-Can Halogen
Bulbs (Included)

U.S. Patent(s): D471,269; D473,639; D475,776

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
5,668	82	69.12



WCS212

Full Function Wall Control System Included
For Details See Page(s): 233

Airus™ is poetry in motion.
Its graceful silhouette
comfortably fits in any
transitional setting. Featured
uplight can be controlled
independently of the halogen
light below.

Lifetime
WARRANTY

WallControl
FULL FUNCTION



F598-WH

White Finish
High Gloss White Blades
with Acid Etched Glass



F598-BN

Brushed Nickel Finish
Silver Blades
with Acid Etched Glass



F513-BN

Brushed Nickel Finish
Dark Walnut Blades

Features:

- 14° Blade Pitch
- 4-Blades 52" Sweep
- 3½" and 6" Downrods
- Full Function Hand Held Remote Control System
- ENERGY STAR® Light Kits Available (Part #K9380-1 and #K9380-2 Page(s): 239)

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
6,230	73	85.25

Lifetime WARRANTY

Remote CONTROL
FULL FUNCTION



F513-ORB

Oil Rubbed Bronze Finish
Medium Maple Blades



RCS212

Full Function Hand Held Remote Control Included
For Details See Page(s): 232



New Era

Traditional in styling,
yet defined by
simple, soft lines.



F513-WH

White Finish
White Blades



F513-KA

Kocoa Finish
Reversible Toned Medium Maple / Dark Maple Blades
(Shown with Toned Medium Maple Blades)



F701-PW

□ Pewter Finish
Natural Walnut Blades
with Etched Marble Glass

Features:

- 14° Blade Pitch
- 5-Blades 52" Sweep
- 3½" and 6" Downrods
- Wall Control System
Independent Up/Downlight
- Integrated Uplight
Use 6-15W Candelabra Bulbs
(Included)
- Integrated Halogen Downlight
Uses 2-50W Mini-Can Halogen Bulbs
(Included)



F701-DRB

□ Dark Restoration Bronze™ Finish
Dark Walnut Blades
with Rustic Scavo Glass

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
5,278	72	73.31



WCS213

□ Wall Control System Control Included
For Details See Page(s): 233

Delano[®]

F701-PN

Polished Nickel Finish
Silver Blades
with White Frosted Glass

F701-KA

Kocoo Finish
Reversible Toned Medium Maple / Dark Walnut Blades
with Rustic Scavo Glass
(Shown with Toned Medium Maple Blades)

F701-DRF

Driftwood Finish
Driftwood Blades
with Bone White Glass

Delano® II



F711-DRB

Dark Restoration Bronze™ Finish
Dark Walnut Blades
with Rustic Scavo Glass

Features:

- 14° Blade Pitch
- 5-Blades 52" Sweep
- Flush Mount - Ideal for Low Ceilings
Less than 11" Drop from Ceiling
- Full Function Wall Control System
- Integrated Halogen Light
Uses 2-50W Mini-Can Halogen Bulbs (Included)

U.S. Patent(s): D595,403; D597,655

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
5,634	70	80.49



WCS212

Full Function Wall Control System Included
For Details See Page(s): 233

Inspired by a long-time favorite, the Delano® II offers the same clean, neo-transitional look but with less than an 11-inch drop from the ceiling.

Lifetime
WARRANTY

WallControl
FULL FUNCTION



F711-PN

Polished Nickel Finish
Silver Blades
with White Frosted Glass



F711-PW

Pewter Finish
Natural Walnut Blades
with Etched Marble Glass



F672-WH/BN

White / Brushed Nickel Finish
White Blades
with Acid Etched Glass

Shown with Cap for Non-Light Use

Features:

- 14° Blade Pitch
- 5-Blades 60" Sweep
- 3½" and 6" Downrods
- Integrated Halogen Light
Uses 1-50W GU10 Halogen Bulb
(Included)
- Full Function Hand Held Remote
Control
- Cap for Non-Light Use (Included)

U.S. Patent(s): Pending

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
7,065	80	88

Lifetime
WARRANTY

Remote
CONTROL



RCS212

Full Function Hand Held Remote Control Included
For Details See Page(s): 232



F672-ORB

Oil Rubbed Bronze
Reversible Medium Maple / Dark Maple Blades
with Acid Etched Glass
(Shown with Medium Maple Blades)

Shown with Cap for Non-Light Use

□ **F672-ORB/AB**

Oil Rubbed Bronze / Antique Brass Finish
Reversible Medium Maple / Dark Maple Blades
with Acid Etched Glass
(Shown with Dark Maple Blades)

Classic lines combined with advanced technology provide our traditional customers with a work horse that transcends time and will perform for many years to come. Die cast blade irons and face plate give a three-dimensional effect. Full function remote control included.

□ **F672-MBK/BN**

Matte Black / Brushed Nickel Finish
Reversible Medium Maple / Dark Maple Blades
with Acid Etched Glass
(Shown with Dark Glass)

Shown with Cap for Non-Light Use



F614-DBB

Dark Brushed Bronze Finish
Dark Maple Blades

Features:

- 14° Blade Pitch
- 5-Blades 54" Sweep
- 3½" and 6" Downrods
- 3-Speed Pull Chain
- Universal Light Kit Adaptable (Sold Separately. Page(s): 239)
- Custom Light Kit K9614 Available (Sold Separately. Page(s): 245)

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
6,257	70.5	89

A smooth blend of finish and form distinguishes the Timeless fan, enhanced by simple clean lines and a unique blade iron design.



Timeless



F614-MCG

Mottled Copper with Gold Highlights Finish
Dark Walnut Blades



F614-PI

Patina Iron Finish
Dark Maple Blades



F614-PW

- Pewter Finish
Dark Walnut Blades

Features:

- 14° Blade Pitch
- 5-Blades 54" Sweep
- 3½" and 6" Downrods
- 3-Speed Pull Chain
- Universal Light Kit Adaptable
(Sold Separately. Page(s): 239)
- Custom Light Kit K9614 Available
(Sold Separately. Page(s): 245)

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
6,257	70.5	89



F614-FB

- French Beige Finish
Medium Maple Blades



Timeless

A smooth blend of finish and form distinguishes the Timeless fan, enhanced by simple clean lines and a unique blade iron design.



F614-ORB

Oil Rubbed Bronze Finish
Medium Maple Blades



F689-KA

Kocoa Finish
Reversible Toned Medium Maple / Dark Maple Blades
(Shown with Toned Medium Maple Blades)

The Kola-XL 60-inch fan features the same design elements as the Kola 52-inch. It has been upgraded to provide the performance necessary for larger rooms and has the convenience of a remote control system.



F689-PW

Pewter Finish
Reversible Dark Maple / Dark Walnut Blades
(Shown with Dark Maple Blades)

Kola-XL



F689-WH

White Finish
White Blades



F689-DBB

Dark Brushed Bronze Finish
Reversible Dark Maple / Dark Walnut Blades
(Shown with Dark Walnut Blades)

Features:

- 12° Blade Pitch
- 60" 5-Blades
- 3½" and 6" Downrods
- Full Function Hand Held Remote Control System
- Universal Light Kit Adaptable (Sold Separately, Page(s): 239)

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
7,557	84.6	89



RCS212

Full Function Hand Held Remote Control Included
For Details See Page(s): 232

Lifetime
WARRANTY

Remote
CONTROL
FULL FUNCTION





F688-PW

Pewter Finish
Reversible Dark Maple / Dark Walnut Blades
(Shown with Dark Maple Blades)

Features:

- 12° Blade Pitch
- 5-Blades 52" Sweep
- 3½" and 6" Downrods
- 3-Speed Pull Chain
- Universal Light Kit Adaptable
(Sold Separately. Page(s): 239)

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
6,002	71.3	84



F688-KA

Cocoa Finish
Reversible Toned Medium Maple / Dark Maple Blades
(Shown with Toned Medium Maple Blades)



Kola



F688-WH

White Finish
White Blades

Smooth lines with a sleek blade iron design and a robust body make the Kola a perfect complement to any home décor.



F688-DBB

Dark Brushed Bronze Finish
Reversible Dark Maple / Dark Walnut Blades
(Shown with Dark Walnut Blades)



F696-CC

Cognac Finish
Reversible Natural Walnut / Dark Walnut Blades
(Shown with Natural Walnut Blades)



F696-KA

Kocoa Finish
Reversible Toned Medium Maple / Dark Maple Blades
(Shown with Toned Medium Maple Blades)

Kafé-XL



F696-WH

White Finish
White Blades

Simple elegance defined in rich finishes, the Kafé-XL brings an exciting look with enhanced features to our value collection.



F696-VP

Vineyard Patina Finish
Reversible Dark Maple / Dark Walnut Blades
(Shown with Dark Walnut Blades)



RCS212

Full Function Hand Held Remote Control Included
For Details See Page(s): 232

Features:

- 12° Blade Pitch
- 5-Blades 60" Sweep
- 3½" and 6" Downrods
- Full Function Hand Held Remote Control System
- Universal Light Kit Adaptable (Sold Separately. Page(s): 239)

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
7,557	84.6	89





F695-KA

Kocoa Finish
Reversible Toned Medium Maple / Dark Maple Blades
(Shown with Toned Medium Maple Blades)

Features:

- 12° Blade Pitch
- 5-Blades 52" Sweep
- 3½" and 6" Downrods
- 3-Speed Pull Chain
- Universal Light Kit Adaptable
(Sold Separately. Page(s): 239)

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
6,002	71.3	84

Simple yet elegant in several finishes, the Kafé brings a refreshing look to our transitional collection.



Kafé



F695-CC

Cognac Finish
Reversible Natural Walnut / Dark Walnut Blades
(Shown with Natural Walnut Blades)



F695-WH

White Finish
White Blades



F695-VP

Vineyard Patina Finish
Reversible Dark Maple / Dark Walnut Blades
(Shown with Dark Maple Blades)

Bolo™



Four of our best selling finishes accent this fan, creating a decorative alternative to an everyday need. Includes glass bowl light kit and remote control system.

F620-BN

Brushed Nickel Finish
Dark Walnut Blades
with Etched Swirl Glass

Features:

- 14° Blade Pitch
- 5-Blades 52" Sweep
- 3½" and 6" Downrods
- Hand Held Remote Control System
- Bowl Light Kit
Uses 3-60W Candelabra Bulbs
(Included)
- Cap for Non-Light Use (Included)

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
5,712	74	77.19



RCS213

Hand Held Remote Control Included
For Details See Page(s): 232



F620-ORB

Oil Rubbed Bronze Finish
Medium Maple Blades
with Excavation Glass





F620-DBB

Dark Brushed Bronze Finish
Dark Maple Blades
with Avorio Mezzo™ Glass



F620-BCW

Belcaro Walnut™ Finish
Dark Walnut Blades
with Excavation Glass

Great Room Traditional



F539-BCW

Belcaro Walnut™ Finish
Dark Walnut Blades

Features:

- 14° Blade Pitch
- 5-Blades 72" Sweep
- 3½" and 6" Downrods
- Full Function Wall Control System
- Universal Light Kit Adaptable
(Sold Separately. See K9376-1 and
K9376-2 on Page(s): 240)
- Quick Connect Switch Cup

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
9,071	106	85.36



WCS212

Full Function Wall Control System Included
For Details See Page(s): 233

Great Room interiors require new ways to manage air. We have accomplished this with expanded blade spans, larger motors and enhanced housings in styles designed to complement those rooms.

Lifetime
WARRANTY

WallControl
FULL FUNCTION



F539-ORB

Oil Rubbed Bronze Finish
Dark Walnut Blades



F539-BN

Brushed Nickel Finish
Dark Walnut Blades

Santa Lucia™

minkaAire®
A Minka Group® Co.



F820-CT

Cattera Bronze™ Finish
Dark Walnut Blades
with Cognac Fluted Etched Glass



Features:

- 14° Blade Pitch
- 5-Blades 60" Sweep
- 3½" and 6" Downrods
- Full Function Wall Control System with Independent Up/Downlight Control
- Integrated Uplight
Uses 5-15W Candelabra Bulbs (Included)
- Integrated Halogen Downlight
Uses 2-50W Mini-Can Halogen Bulbs (Included)



F820-IBR

Illuminati Bronze™ Finish
Dark Walnut Blades
with Silver Patina Glass

U.S. Patent(s): D556,882; D559,436; D568,984;
D570,986; D574,948; D599,000; D599,466;
5,554,006
© 2006 Minka Lighting, Inc.

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
6,936.7	84	82.58



WCS212

Full Function Wall Control System Included
For Details See Page(s): 233



CM8222-IBR 22"

Illuminati Bronze™ Finish
22" Diameter
Matching Ceiling Medallion for F820-IBR
© 2005 Minka Lighting, Inc.

Lifetime
WARRANTY

WallControl
FULL FUNCTION



F812-10

Iron Oxide Finish
Dark Walnut Blades
with Venetian Scavo Glass

Simple, clean, architectural lines have been utilized to define the Lineage™.

Features:

- 14° Blade Pitch
- 5-Blades 54" Sweep
- 3½" and 6" Downrods
- Full Function Wall Control System Independent Up/Downlight
- Integrated Uplight
Uses 6-15W Candelabra Bulbs (Included)
- Integrated Downlight
Uses 2-60W Candelabra Bulbs (Included)
- Complements Lighting Available Through Minka-Lavery®

U.S. Patent(s): D528,652; D531,298; D532,098; D533,292; D535,012; D563,540

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
6,534	100	65.34



WCS212

Full Function Wall Control System Included
For Details See Page(s): 233

Lifetime
WARRANTY

WallControl
FULL FUNCTION



F705-STW

Sterling Walnut™ Finish
Sterling Walnut™ Shaded Blades
with Aged Champagne Glass

Features:

- 14° Blade Pitch
- 5-Blades 56" Sweep
- 3½" and 12" Downrods
- Full Function Wall Control System
- Integrated Halogen Light
Uses 2-50W Mini-Can Halogen
Bulbs (Included)

U.S. Patent(s): D513,532; D514,685; D514,690;
D516,702; D521,627; D522,122

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
6,765	93	72



WCS212

- Full Function Wall Control System Included
For Details See Page(s): 233



CM7022-TSP 22"

- Tuscan Patina™ Finish
Matching Ceiling Medallion for F705/F715
© 2005 Minka Lighting, Inc.

- Also Available:
CM7022-STW 22"

Sterling Walnut™ Finish



CM7038-STW 38"

- Sterling Walnut™ Finish
Matching Ceiling Medallion for F705/F715
© 2005 Minka Lighting, Inc.

Lifetime
WARRANTY

WallControl
FULL FUNCTION



F715-TSP

Tuscan Patina™ Finish
Tuscan Patina™ Shaded Blades
with Aged Champagne Glass

Features:

- 14° Blade Pitch
- 5-Blades 68" Sweep
- 3½" and 12" Downrods
- Full Function Wall Control System
- Integrated Halogen Light
Uses 2-50W Mini-Can Halogen
Bulbs (Included)

U.S. Patent(s): D513,532; D514,685; D514,690;
D516,702; D521,627; D522,122

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
7,581	104	72.84

Lifetime
WARRANTY

WallControl
FULL FUNCTION



F715-STW


Sterling Walnut™ Finish
Sterling Walnut™ Shaded Blades
with Aged Champagne Glass



WCS212

Full Function Wall Control System Included
For Details See Page(s): 233

Classica



F759-PBL Gallery Edition

Provencal Blanc Finish
Provencal Blanc Blades
with Etched Glass

Includes:
Integrated 3-Light Kit
Uses 3-60W Candelabra Bulbs
(Included)
Hand Held Remote Control System

Lifetime
WARRANTY

Remote
CONTROL
FULL FUNCTION

Features:

- 14° Blade Pitch
- 5-Blades 54" Sweep
- 3½" and 6" Downrods
- 3-Speed Pull Chain
- Universal Light Kit Adaptable
(Sold Separately. Page(s): 239)
- Custom Light Kit K9659 Available
(Sold Separately. Page(s): 245)

Old world hand-painted finishes accentuate the hand-carved details to create a traditional European style fan.

© 2009 Minka Lighting, Inc.

Energy Information (Excludes Lights)


Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
6,313	71.6	88.17

Lifetime
WARRANTY



F659-PBL

Provencal Blanc Finish
Provencal Blanc Blades





□ **F659-BCW**

Belcaro Walnut™ Finish
Dark Walnut Blades



□ **F659-FB**

French Beige Finish
Medium Maple Blades



□ **F659-DRF**

Driftwood Finish
Driftwood Blades



□ **F659-PI**

Patina Iron Finish
Dark Walnut Blades

Volterra™

minkaAire®
A Minka Group® Co.



F702-BCW

Belcaro Walnut™ Finish
Natural Walnut Blades
with Aged Champagne Glass

Volterra™ is a neo-classical inspiration, incorporating an uplight with an integrated halogen downlight.

Features:

- 14° Blade Pitch
- 5-Blades 52" Sweep
- 3½" and 6" Downrods
- Wall Control System Independent Up/Downlight
- Integrated Uplight Uses 6-15W Candelabra Bulbs (Included)
- Integrated Halogen Downlight Uses 2-50W Mini-Can Halogen Bulbs (Included)

© 2002 Minka Lighting, Inc.

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
5,425	67	80.97



F702-VB

Volterra Bronze™ Finish
Natural Walnut Blades
with French Scavo Glass



WCS213

Wall Control System Included
For Details See Page(s): 233

Lifetime
WARRANTY

WallControl



F544-BCW

Belcaro Walnut™ Finish
Dark Walnut Blades
with Aged Champagne Glass



F544-GBZ

Golden Bronze Finish
Dark Walnut Blades
with Excavation Glass

Features:

- 14° Blade Pitch
- 5-Blades 52" Sweep
- Flush Mount - Ideal for Low Ceilings
Less than 11" Drop from Ceiling
- Hand Held Remote Control System
- Integrated Light
Uses 2-60W Candelabra Bulbs
(Included)

U.S. Patent(s): D526,714; D527,094; D530,415;
D532,896; D536,777

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
6,050	79.8	75.81

Elegance, style and performance for low ceiling applications, this fan has less than an 11-inch drop from ceiling to cap.



RCS213

Hand Held Remote Control Included
For Details See Page(s): 232

Lifetime
WARRANTY

Remote
CONTROL



Features:

- 14° Blade Pitch
- 5-Blades 68" Sweep
- 3½" and 16" Downrods
- Full Function Wall Control System with Independent Up/Downlight Control Feature
- Precision Machine Cut and Polished Lead-Free SPECTRA® CRYSTAL
- Integrated Uplight
Uses 5-15W Candelabra Bulbs (Included)
- Integrated Halogen Downlight
Uses 2-50W Mini-Can Halogen Bulbs (Included)

© 2005 Minka Lighting, Inc.

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
6,022	95	63.39



WCS212

- Full Function Wall Control System Included
For Details See Page(s): 233

F900-BCW

- Belcaro Walnut™ Finish
Dark Walnut Blades
with Etched Cut Glass

Shown with Optional GC900 SET
MADE WITH SPECTRA® CRYSTAL



F900-BCW

- Belcaro Walnut™ Finish
Dark Walnut Blades
with Etched Cut Glass

Lifetime
WARRANTY

WallControl
FULL FUNCTION



Traditional Gyro™



F502-PBL

Provençal Blanc Finish
Provençal Blanc Blades
Pearl White Glass



A magnificent rendition of the original Gyro™ design, the traditional finish transcends the turns of time.



F502-BCW

Belcaro Walnut™ Finish
Belcaro Walnut™ Blades
with Belcaro Walnut™ Glass



WCS212

Full Function Wall Control System Included
For Details See Page(s): 233

Features:

- High Performance Twin Turbofans Total Sweep 42"
- 20° Blade Pitch
- 4½" and 12" Downrods
- 1,000 - 1,500 R.P.M. Fan Speeds
- Turbofan Heads Adjustable Up and Down
- Complete Assembly Rotates 360° at 3 R.P.M.
- Full Function Wall Control System Incorporating Fully Independent Fan Head Speeds and Axis Rotation
- Integrated Halogen Light Uses 1-100W Mini-Can Halogen Bulb (Included)
- Cap for Non-Light Use (Included)

U.S. Patent(s): D523,548; D523,549; D523,550; D523,983; D524,438; D526,059; D526,400; D526,712; D530,810; D532,097; D567,350; 6,832,902; 7,183,680; 7,229,255
© 2004 Minka Lighting, Inc.

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
5,050	102	49.51

Lifetime
WARRANTY

WallControl
FULL FUNCTION

Cage Free Gyro™

with LED Light



Gyro Fans Rotate 360°

Features:

- High Performance Twin Turbofans Total Sweep 37"
- 23° Blade Pitch
- 3½" and 6" Downrods
- 1,000 - 1,500 R.P.M. Fan Speeds
- Turbofan Heads Adjustable Up and Down
- Complete Assembly Rotates 360° at 3 R.P.M.
- Full Function Wall Control System Incorporating Fully Independent Fan Head Speeds and Axis Rotation
- Integrated LED Light Uses 16W LED (Included) 3 Year Warranty
- 1,352 Lumens
- 2,700K
- CRI 80

U.S. Patent(s): 6,832,902; 7,183,680; 7,229,255
Additional U.S. Patent(s) Pending

* Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
3,000	45	66

* Estimated



WCS212

Full Function Wall Control System Included
For Details See Page(s): 233

A wonderful addition to our Gyro™ series. Simple, clean design featuring twin turbo fans, 16 watt LED* and cage free blades allow for a classic transitional spirit.

F304L-BN/SL

Brushed Nickel Finish
Silver Blades
with Etched Opal Glass



Gyro Fans Rotate 360°

F304L-ORB/MM

Oil Rubbed Bronze Finish
Medium Maple Blades
with Etched Opal Glass

Elemental Gyro™

with LED Light



F306L-BS/SL

Brushed Steel Finish
Silver Blades
with Etched Opal Glass

Gyro Fans
Rotate 360°

Elemental Gyro™ is the newest addition to our Gyro™ series. A clean, industrial spirit combined with a LED* light source and Etched Opal glass. The Gyro™ series continues to offer air movement throughout the entire room, or can be stopped to position air in only one area. Adjustable fan cages further enhance air movement.



Gyro Fans
Rotate 360°

F306L-ORB/MM

Oil Rubbed Bronze Finish
Medium Maple Blades
with Etched Opal Glass

Features:

- High Performance Twin Turbofans
Total Sweep 42"
- 23° Blade Pitch
- 3½" and 6" Downrods
- 1,000 - 1,500 R.P.M. Fan Speeds
- Turbofan Heads Adjustable Up and Down
- Complete Assembly Rotates 360° at 3 R.P.M.
- Full Function Wall Control System Incorporating Fully Independent Fan Head Speeds and Axis Rotation
- Integrated LED Light Uses 16W LED (Included) 3 Year Warranty
- 1,352 Lumens
- 2,700K
- CRI 80

U.S. Patent(s): 6,832,902; 7,183,680; 7,229,255
Additional U.S. Patent(s) Pending

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
3,000	45	66

* Estimated



WCS212

Full Function Wall Control System Included
For Details See Page(s): 233



* LED (Light Emitting Diodes)



Gyro Fans
Rotate 360°

F802-KA

Kocoa Finish
Kocoa Blades
with Tinted Opal Glass

An addition to our popular Gyro™ family, the Vintage Gyro™ performs with the same efficiency and unsurpassed level of comfort as our other Gyro™ models, but with an early 20th Century style.

Vintage Gyro™



F802-BN/CH

Brushed Nickel / Chrome Finish
Rosewood Blades
with Etched Opal Glass

Gyro Fans
Rotate 360°



F802-ORB

Oil Rubbed Bronze Finish
Oil Rubbed Bronze Blades
with Tinted Opal Glass

Gyro Fans
Rotate 360°



WCS212

Full Function Wall Control System Included
For Details See Page(s): 233

Features:

- High Performance Twin Turbofans
Total Sweep 42"
- 20° Blade Pitch
- 3½" and 6" Downrods
- 720 - 1,350 R.P.M. Fan Speeds
- Turbofan Heads Adjustable Up and Down
- Complete Assembly Rotates 360°
at 3 R.P.M.
- Full Function Wall Control System
Incorporating Fully Independent
Fan Head Speeds and Axis
Rotation
- Integrated Halogen Light
Uses 1-100W Mini-Can Halogen
Bulb (Included)
- Cap for Non-Light Use (Included)

U.S. Patent(s): 6,832,902; 7,183,680; 7,229,255

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
5,050	102	49.51

Lifetime
WARRANTY

WallControl
FULL FUNCTION

Gyro™

minkaAire®
A Minka Group® Co.



F602-BN/CH

Brushed Nickel / Chrome Finish
with Chrome Accents and Cages
Rosewood Blades
with Etched Opal Glass

Features:

- High Performance Twin Turbofans
Total Sweep 42"
- 20° Blade Pitch
- 3½" and 6" Downrods
- 720 - 1,350 R.P.M. Fan Speeds
- Turbofan Heads Adjustable Up and Down
- Complete Assembly Rotates 360°
at 3 R.P.M.
- Full Function Wall Control System
Incorporating Fully Independent
Fan Head Speeds and Axis
Rotation
- Integrated Halogen Light
Uses 1-100W Mini-Can Halogen
Bulb (Included)
- Cap for Non-Light Use (Included)

U.S. Patent(s): D478,975; D489,443, D490,146;
6,832,902; 7,183,680; 7,229,255

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
5,050	102	49.51



WCS212

Full Function Wall Control System Included
For Details See Page(s): 233

A truly unique design offering an unsurpassed level of comfort. The Gyro™ fan's ability to precisely control the direction and intensity of the cooling breeze efficiently circulates air in any environment.



F602-RRB

Restoration Bronze™ Finish
Restoration Bronze™ Blades
with Etched Opal School House Globe Glass

Lifetime
WARRANTY

WallControl
FULL FUNCTION

Gyro™ Wet



F402-ORB

Oil Rubbed Bronze Finish
Oil Rubbed Bronze Blades
with Etched Opal School House Globe Glass



Capturing the design elements of the original Gyro™, the Gyro™ Wet provides unsurpassed performance and comfort levels in the toughest environments. Rotating 360°, and controlled by a wall control system, it offers wonderful cooling in any area and the option to stop and redirect air for maximum benefit.


Features:

- High Performance Twin Turbofans Total Sweep 42"
- 20° Blade Pitch
- Complete Assembly Rotates 360° at 3 R.P.M.
- 720 - 1,350 R.P.M. Fan Speeds
- Turbofan Heads Adjustable Up and Down
- Galvanized Steel 3½" and 6" Downrods
- Full Function Wall Control System Incorporating Fully Independent Fan Head Speeds and Lighting Fixture
- Integrated Halogen Light Uses 1-100W Mini-Can Halogen Bulb (Included)
- Cap for Non-Light Use (Included)
- Indoor/Outdoor Use UL Listed for Wet Locations

U.S. Patent(s): D478,975; D489,443; D489,809; D490,146; 6,832,902; 7,183,680; 7,229,255

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
5,050	102	49.51



WCS212

Full Function Wall Control System Included
For Details See Page(s): 233



F402-BNW

Brushed Nickel Wet Finish
Silver Blades
with Etched Opal Glass

Shown with Cap for Non-Light Use

Lifetime
WARRANTY

WallControl
FULL FUNCTION



LISTED
For Wet Location

Gyrette™



F302-RRB

Restoration Bronze™ Finish
Restoration Bronze™ Blades



The Gyrette™ captures the design elements of the original Gyro™ in a smaller format. We have utilized flexible arms to maximize air circulation.

Features:

- High Performance Twin Turbofans Total Sweep 36"
- Adjustable Turbofan Heads
- 14° Blade Pitch
- Complete Assembly Rotates 360° at 3 R.P.M.
- 3-Speeds: 800, 1,090, 1,470 R.P.M.
- 30° Flexible Arms
- 4½" Downrod
- Full Function Hand Held Remote Control System



F302-BN

Brushed Nickel Finish
Brushed Nickel Blades

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
1,480	58	25.52



RCS212

Full Function Hand Held Remote Control Included
For Details See Page(s): 232





F582-BNW

Brushed Nickel Wet Finish
Silver Blades
with Acid Etched Glass

Indoor/Outdoor Collection

Minka-Aire® recognizes a need in today's al fresco lifestyle by offering an Outdoor Series of ceiling fans. All are UL or ETL Listed for wet location usage, making these fans perfect for patios, porches, and other exposed areas. Motor housings and blades are fully protected against water and all weather conditions. Particular models have a combined waterproof light kit to provide additional lighting outdoors. These fans feature various designer finishes to complement your patio furniture.

Now you are able to enjoy a wonderful breeze on your patio, in your gazebo or over your outdoor spa! Of course, you may use all of these models indoors as well.

GEORGE
KOVACS®

by

minkaAire®
A Minka Group® Co.

Slipstream XXL is the second generation of our uniquely designed 8-blade fan. Slipstream XXL has grown to 84 inches, making this a power house of air flow and designed with enough presence to be used in both residential and commercial environments. In addition, it has a UL listing for both indoor and outdoor spaces.



F889-ORB

Oil Rubbed Bronze Finish
Oil Rubbed Bronze Blades
with Tinted Opal Glass

Shown with Cap for Non-Light Use



F889-SI

Smoked Iron Finish
Smoked Iron Blades
with Etched Opal Glass

Slipstream XXL



F889-BNW

Brushed Nickel Wet Finish
Silver Blades
with Etched Opal Glass

Features:

- 14° Blade Pitch
- 8-Concave Blades 84" Sweep
- DC 165 x 25mm Motor
- Galvanized Steel
3½" and 6" Downrods
- Stainless Steel Hardware and
All Weather Blades
- Special Hand Held Remote Control
System Included - RC400
- Integrated Light
Uses 1-26W GU24 Non-Dimmable
CFL (Included)
- Cap for Non-Light Use (Included)
- Indoor/Outdoor Use
UL Listed for Wet Locations

U.S. Patent(s): D715,917



DC MOTOR

Lifetime
WARRANTY

Remote
CONTROL
FULL FUNCTION



RC400

Full Function Hand Held Remote Control Included
For Details See Page(s): 232

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
11,022	26.8	411.27



Slipstream



F888-BNW

Brushed Nickel Wet Finish
Silver Blades
with Etched Opal Glass

Features:

- 14° Blade Pitch
- 8-Concave Blades 65" Sweep
- DC 165 x 25mm Motor
- Galvanized Steel
3½" and 6" Downrods
- Stainless Steel Hardware and
All Weather Blades
- Special Hand Held Remote Control
System Included - RC400
- Integrated Light
Uses 1-18W GU24 Non-Dimmable
Squat CFL (Included)
- Cap for Non-Light Use (Included)
- Indoor/Outdoor Use
UL Listed for Wet Locations



RC400

Full Function Hand Held Remote Control Included
For Details See Page(s): 232

DC MOTOR

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
8,778	27.6	318.04

Streamlined industrial styling destined this 8-bladed wonder to make a cool statement in any indoor or outdoor setting.

U.S. Patent(s): D715,917



LISTED
For Wet Location





F888-WHF

Flat White Finish
Flat White Blades
with Etched Opal Glass



F888-DK

Distressed Koa Finish
Distressed Koa Blades
with Tinted Opal Glass



F888-ORB

Oil Rubbed Bronze Finish
Oil Rubbed Bronze Blades
with Tinted Opal Glass

Shown with Cap for Non-Light Use

Simple



F787-ORB

Oil Rubbed Bronze Finish
Medium Maple Blades

Features:

- 14° Blade Pitch
- 3-Blades 52" Sweep
- DC 123 x 30mm Motor
- 3½" and 6" Downrods
- Special Hand Held Remote Control System Included - RC400
- Custom 15W LED Light Kit K9787L Available (Sold Separately. Page(s): 244)
- Indoor/Outdoor Use
ETL Listed for Wet Locations

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
7,051	33.1	213

So simple! We gave this wonderful design a name that best denotes it's spirit! Incredibly delicate and merely invisible. This design best displays the advancement in technology with indoor/outdoor use, DC motor, optional LED* light kit and a hand held remote.

Lifetime
WARRANTY

Remote
CONTROL
FULL FUNCTION



DC MOTOR


RC400

Full Function Hand Held Remote Control Included
For Details See Page(s): 232



Intertek
For Wet Location





F787-SL

□ Silver Finish
Silver Blades
Shown with Optional K9787L-SL
LED Light Kit



F787-WHF

□ Flat White Finish
Flat White Blades
Shown with Optional K9787L-WHF
LED Light Kit



F681-SDBK/WS

Sand Black / Weathered Steel Finish
Charcoal Driftwood Blades
with Clear Fresnel Lens



F681-BNW

Brushed Nickel Wet Finish
Silver Blades
with Clear Fresnel Lens



F681-WA/PW

Weathered Aluminum / Pewter Finish
Dark Pine Blades
with Clear Fresnel Lens

Groton



F681-ORB

Oil Rubbed Bronze Finish
Dark Pine Blades
with Clear Fresnel Lens

Inspired by the clear Fresnel lens used in lighthouses along the coast of Connecticut, we are introducing our Groton collection. Classic design combined with nautical spirit in various finishes. All which will suit both indoor and outdoor locations, as this fan has a UL wet rating.



F681-PN

Polished Nickel Finish
Silver Blades
with Clear Fresnel Lens
(Finish For Indoor Use Only)



RCS212

Full Function Hand Held Remote Control Included
For Details See Page(s): 232

Features:

- 12° Blade Pitch
- 5-Blades 56" Sweep
- 10" Downrod
- Full Function Hand Held Remote Control System
- Integrated Halogen Light
Uses 2-50W Mini-Can Halogen Bulbs (Included)
- Indoor/Outdoor Use
UL Listed for Wet Locations

U.S. Patent(s): Pending

* Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
6,500	90	72

* Estimated

Lifetime
WARRANTY

Remote
CONTROL
FULL FUNCTION



LISTED
For Wet Location



Roto XL



F624-ORB

- Oil Rubbed Bronze Finish
- Oil Rubbed Bronze Blades

Features:

- 20° Blade Pitch
- 3-Blades 62" Sweep
- 4½" and 6" Downrods
- Aluminum Construction
- Converts to Electronic Control System
- Indoor/Outdoor Use - ETL Listed for Wet Locations

U.S. Patent(s): D750,221
Additional U.S. Patent(s) Pending



WC115-WH

Wall Control System Included
For Details See Page(s): 233

Energy Information

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
7,567	70.69	107.04

Lifetime
WARRANTY

Remote
CONTROL
FULL FUNCTION


ETL
US
Intertek
For Wet Location





F624-ABD

Brushed Aluminum Finish
Silver Blades



Roto XL features a sleek and contemporary design with a classic industrial look. Well edited; an impeccably executed design features a slight "fold" construction along the length of the blades to increase the flow of air. A perfect marriage of form and function. Roto XL features a full 62-inch spread combined with a wet location specification use for indoor or outdoors.



F624-WHF

Flat White Finish
Flat White Blades

See Page 44 for Roto Family

Concept™ I Wet 58"

STAINLESS STEEL



F477-ORB

Oil Rubbed Bronze Finish
Oil Rubbed Bronze Blades
with Pietra Glass

Features:

- 14° Blade Pitch
- 3-Blades 58" Sweep
- **Marine Grade Stainless Steel Construction**
- Stainless Steel
3½" and 6" Downrods
- Full Function Wall Control System
- Integrated Halogen Light
Uses 1-100W Mini-Can Halogen
Bulb (Included)
- Indoor/Outdoor Use
UL Listed for Wet Locations
- Cap for Non-Light Use (Included)

U.S. Patent(s): D475,782; D476,408; D478,654;
D478,980; 7,008,192

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
7,026	65.4	107.43



F477-WH

White Finish
White Blades
with White Opal Glass

Shown with Cap for Non-Light Use



WCS212

Full Function Wall Control System Included
For Details See Page(s): 233

Lifetime
WARRANTY

WallControl
FULL FUNCTION



LISTED

For Wet Location



STAINLESS STEEL



F477-BNW

Brushed Nickel Wet Finish
Silver Blades
with White Opal Glass

Shown with Cap for Non-Light Use

STAINLESS STEEL

UL listed for use indoors and outdoors, furthering the versatility and timeless perfection that is the Concept™ I series. Concept™ I Wet is constructed of marine grade stainless steel to ensure long lasting appearance and function in the toughest environments.

STAINLESS STEEL

Concept™ I Wet 52"



F577-BNW

Brushed Nickel Wet Finish
Silver Blades
with White Opal Glass

Features:

- 14° Blade Pitch
- 3-Blades 52" Sweep
- Galvanized Steel
3½" and 6" Downrods
- Construction Grade Polymer
- Full Function Wall Control System
- Integrated Halogen Light
Uses 1-100W Mini-Can Halogen
Bulb (Included)
- Indoor/Outdoor Use
UL Listed for Wet Locations
- Cap for Non-Light Use (Included)

U.S. Patent(s): D475,782; D476,408; D478,654;
D478,980; 7,008,192

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
5,991	51.2	117.01

Lifetime
WARRANTY

WallControl
FULL FUNCTION



For Wet Location



WCS212

Full Function Wall Control System Included
For Details See Page(s): 233

The Concept™ I ceiling fan collection is the most successful series in the history of Minka-Aire®. It is only natural that we would produce a new version that is UL listed for use indoors and outdoors, furthering the versatility and timeless perfection that is the Concept™ I series.

See Page 74 for Concept™ I Family



F476-ORB

- Oil Rubbed Bronze Finish
- Taupe Blades
- with Pietra Glass



F476-WH

- White Finish
- White Blades
- with White Opal Glass

Shown with Cap for Non-Light Use



F474-ORB

Oil Rubbed Bronze Finish
Taupe Blades
with Pietra Glass



F474-WH

White Finish
White Blades
with White Opal Glass
Shown with Cap for Non-Light Use

Concept™ II Wet 52"

F574-BNW

Brushed Nickel Wet Finish
Silver Blades
with White Opal Glass

As the name implies, the Concept™ II Wet ceiling fan is “a taste of things to come.” Simple in style, yet ingenious by design and UL Listed for wet locations.

Features:

- 14° Blade Pitch
- 3-Concave Blades 52" Sweep
- Flush Mount - Ideal for Low Ceilings
Total Hanging Depth 12"
- Construction Grade Polymer
- Full Function Wall Control System
- Integrated Halogen Light
Uses 1-100W Mini-Can Halogen Bulb (Included)
- Cap for Non-Light Use (Included)
- Indoor/Outdoor Use
UL Listed for Wet Locations
(Will Not Pendulum In Windy Conditions)

U.S. Patent(s): D478,654; D478,974; D478,980; 7,008,192

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
6,053	51.3	117.99



WCS212

Full Function Wall Control System Included
For Details See Page(s): 233

See Page 76 for Concept™ II Family

Lifetime
WARRANTY

WallControl
FULL FUNCTION



For Wet Location



Traditional Concept™ 52"



F594-ORB

Oil Rubbed Bronze Finish
Medium Maple Blades
with Tinted Opal Glass

Features:

- 14° Blade Pitch
- 3-Blades 52" Sweep
- Flush Mount - Ideal for Low Ceilings
Total Hanging Depth 11"
- Full Function Wall Control System
- Integrated Halogen Light
Uses 1-100W Mini-Can Halogen Bulb (Included)
- Indoor/Outdoor Use
UL Listed for Wet Locations
- Cap for Non-Light Use (Included)

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
6,565	61	108.52

A variation on our best selling contemporary Concept™ II fan, this fan provides the same superb styling for your more traditional indoor and outdoor settings.



WCS212

Full Function Wall Control System Included
For Details See Page(s): 233

Lifetime
WARRANTY

WallControl
FULL FUNCTION



LISTED
For Wet Location





F594-PW

Pewter Finish
Dark Maple Blades
with Opal Glass



F594-WH

White Finish
White Blades
with Opal Glass

Traditional Concept™ 44"

F593-PW

Pewter Finish
Dark Maple Blades
with Opal Glass

Features:

- 14° Blade Pitch
- 3-Blades 44" Sweep
- Flush Mount - Ideal for Low Ceilings
Total Hanging Depth 11"
- Full Function Wall Control System
- Integrated Halogen Light
Uses 1-100W Mini-Can Halogen Bulb (Included)
- Indoor/Outdoor Use
UL Listed for Wet Locations
- Cap for Non-Light Use (Included)

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
4,940	49	100

Lifetime
WARRANTY

WallControl
FULL FUNCTION



LISTED
For Wet Location



WCS212

Full Function Wall Control System Included
For Details See Page(s): 233

A variation on our best selling contemporary Concept™ II fan, this fan provides the same superb styling for your more transitional indoor and outdoor settings.



□ **F593-ORB**

Oil Rubbed Bronze Finish
Medium Maple Blades
with Tinted Opal Glass



□ **F593-WH**

White Finish
White Blades
with Opal Glass

Shown with Cap for Non-Light Use

LED

F753L-BNW

Brushed Nickel Wet Finish
Silver Blades
with Etched Opal Glass

Minka-Aire's "everywhere" fan with a unique contemporary twist that is suitable for all indoor or outdoor environments. The Java LED features an integrated 17 watt LED* light.

LED

F753L-WHF

Flat White Finish
Flat White Blades
with Etched Opal Glass

Java LED

with LED Light

LED

F753L-KA

Kocoa Finish
Kocoa Blades
with Etched Opal Glass

Features:

- 15° Blade Pitch
- 3-Blades 54" Sweep
- 3½" and 6" Downrod
- Hand Held Remote Control System
- Integrated LED Light
Uses 17W LED (Included)
3 Year Warranty
- 1,350 Lumens
- 3,000K
- CRI 80
- Indoor/Outdoor Use - UL Listed for Wet Locations

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
5,682	47	121

F753L-PN

Polished Nickel Finish
Silver Blades
with Etched Opal Glass
(Finish For Indoor Use Only)



RCS213

Hand Held Remote Control Included
For Details See Page(s): 232

Lifetime
WARRANTY

Remote
CONTROL



For Wet Location



See Page 160 for Java Family

Java



F753-KA

Kocoa Finish
Kocoa Blades

Features:

- 14° Blade Pitch
- 3-Blades 54" Sweep
- 3½" and 6" Downrods
- Hand Held Remote Control System
- Indoor/Outdoor Use
UL Listed for Wet Locations

Energy Information

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
5,682	47	121

Minka-Aire's "everywhere" fan with a unique contemporary twist that is suitable for all environments.

Lifetime
WARRANTY

Remote
CONTROL



RCS213

Hand Held Remote Control Included
For Details See Page(s): 232

See Page 158 for Java LED Family



LISTED
For Wet Location





□ **F753-WHF**

Flat White Finish
Flat White Blades



□ **F753-BNW**

Brushed Nickel Wet Finish
Silver Blades

Aluma Wet



F523-ABD

Brushed Aluminum Finish
Silver Blades
with Etched Opal Glass

Shown with Cap for Non-Light Use

Features:

- 12° Blade Pitch
- 4-Blades 52" Sweep
- 3½" and 6" Downrods
- All Aluminum Construction
- Hand Held Remote Control System
- Integrated Halogen Light
Uses 1-100W Mini-Can Halogen
Bulb (Included)
- Indoor/Outdoor Use
UL Listed for Wet Locations
- Cap for Non-Light Use (Included)

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
4,834	51.5	93.88



F523-ORB

Oil Rubbed Bronze Finish
Oil Rubbed Bronze Blades
with Tinted Opal Glass



RCS213

Hand Held Remote Control Included
For Details See Page(s): 232

Lifetime
WARRANTY

Remote
CONTROL



LISTED

For Wet Location





F523-WHF

Flat White Finish
Flat White Blades
with Etched Opal Glass

Aluma Wet is our answer to the fan that goes anywhere and has everything. For use indoors and outdoors, Aluma Wet is UL listed for use in wet locations. Produced from weather resistant materials, the Aluma Wet provides air circulation for every location including patio, porch and pergola.

See Page 54 for Aluma Family

Strata



F734-ORB

Oil Rubbed Bronze Finish
Oil Rubbed Bronze Blades
with Tinted Opal Glass

Features:

- 12° Blade Pitch
- 4-Blades 52" Sweep
- Galvanized Steel
3½" and 6" Downrods
(Uses ¾" I.D. DR5 Series Downrod)
- Hand Held Remote Control System
- Integrated Light
Uses 1-75W Mini-Can Halogen
Bulb (Included)
- Indoor/Outdoor Use
UL Listed for Wet Locations
- Cap for Non-Light Use (Included)

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
5,098	49	104.4

Lifetime
WARRANTY

Remote
CONTROL

UL
LISTED
For Wet Location



RCS213

Hand Held Remote Control Included
For Details See Page(s): 232



F734-ORB

Shown with Cap for
Non-Light Use

The Strata with its Smoked Iron or Galvanized finishes adds a rustic yet contemporary style to your home.



F734-GL

Galvanized Finish
Silver Blades
with Etched Opal Glass



F734-GL

Shown with Cap for
Non-Light Use



F734-SI

Smoked Iron Finish
Smoked Iron Blades
with Etched Opal Glass



F582-ORB

Oil Rubbed Bronze Finish
Taupe Blades
with Vintage Amber Glass



F582-BNW

Brushed Nickel Wet Finish
Silver Blades
with Acid Etched Glass

Rainman™



F582-GL

Galvanized Finish
Silver Blades
with Acid Etched Glass

Reminiscent of lighting often found along shoreline walkways, the Rainman™, as the name suggests, is an excellent choice for exterior as well as interior use.

Features:

- 14° Blade Pitch
- 5-Blades 54" Sweep
- Galvanized Steel
3½" and 6" Downrods
- Stainless Steel Hardware and All Weather Blades
- Wall Control System
- Integrated Halogen Caged Light
Uses 1-100W Mini-Can Halogen Bulb (Included)
- Indoor/Outdoor Use
UL Listed for Wet Locations

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
5,508	58	94.96



WCS213

Wall Control System Included
For Details See Page(s): 233

Lifetime
WARRANTY

WallControl



LISTED
For Wet Location

Gyro™ Wet



Features:

- High Performance Twin Turbofans Total Sweep 42"
- 20° Blade Pitch
- Complete Assembly Rotates 360° at 3 R.P.M.
- 720 - 1,350 R.P.M. Fan Speeds
- Turbofan Heads Adjustable Up and Down
- Galvanized Steel 3½" and 6" Downrods
- Full Function Wall Control System Incorporating Fully Independent Fan Head Speeds and Lighting Fixture
- Integrated Halogen Light Uses 1-100W Mini-Can Halogen Bulb (Included)
- Cap for Non-Light Use (Included)
- Indoor/Outdoor Use UL Listed for Wet Locations

U.S. Patent(s): D478,975; D489,443; D489,809; D490,146; 6,832,902; 7,183,680; 7,229,255

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
5,050	102	49.51




For Wet Location



WCS212

Full Function Wall Control System Included
For Details See Page(s): 233



F402-BNW

Brushed Nickel Wet Finish
Silver Blades
with Etched Opal Glass

Shown with Cap for Non-Light Use

F402-ORB

Oil Rubbed Bronze Finish
Oil Rubbed Bronze Blades
with Etched Opal School House Globe Glass

Capturing the design elements of the original Gyro™, the Gyro™ Wet provides unsurpassed performance and comfort levels in the toughest environments. Rotating 360° and controlled by a wall control system, it offers wonderful cooling in any area and the option to stop and redirect air for maximum benefit.

Shangri-La®



F580-VR/BB

Vintage Rust™ Finish
Bamboo All Weather Blades
Shown with Cap for Non-Light Use

Our wicker design, coupled with a Vintage Rust™ finish, replicates a highly popular tropical motif.

Features:

- 14° Blade Pitch
- 5-Blades 52" Sweep
- Galvanized Steel
3½" and 6" Downrods
- Stainless Steel Hardware and All Weather Blades
- 3-Speed Pull Chain
- Snap Lock/Set Screw Blade Assembly System
- Integrated Halogen Caged Etched Glass Light
Uses 1-100W Mini-Can Halogen Bulb (Included)
- Indoor/Outdoor Use
UL Listed for Wet Location
- Cap for Non-Light Use (Included)

U.S. Patent(s): D501,251; D501,922; D501,923; D502,770; D508,287; D514,215; D522,643; 7,008,192

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
5,375	79	68.03



F580-VR/BB


Vintage Rust™ Finish
Bamboo All Weather Blades
with Caged Etched Glass

Lifetime
WARRANTY

UL
LISTED
For Wet Location



Gauguin™



Features:

- 14° Blade Pitch
- 4-Blades 52" Sweep
- Galvanized Steel
3½" and 6" Downrods
(Uses ¾" I.D. DR5 Series Downrod)
- Stainless Steel Hardware and
All Weather Blades
- Full Function Wall Control System
- Integrated Halogen Light
Uses 1-50W MR16 120V 2-Pin
Halogen Bulb (Included)
- Custom Ceiling Adapter Kit A581
Available
(Sold Separately. Page(s): 238)
- Indoor/Outdoor Use
UL Listed for Wet Locations
- Cap for Non-Light Use (Included)

U.S. Patent(s): D513,319; D514,691; D514,692;
D516,703; D517,201; D519,199

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
4,834	52	92.97

Lifetime
WARRANTY

WallControl
FULL FUNCTION



LISTED

For Wet Location



WCS212

Full Function Wall Control System Included
For Details See Page(s): 233

F581-BG

Bahama Beige™ Finish
Bahama Beige™ Blade
with Etched Glass



F581-BG

Bahama Beige™ Finish
Shown with Optional A581-BG
Ceiling Adapter



F581-WHF

Flat White Finish
Flat White Blades
with Etched Glass

Tropical style influences the Gauguin™ by incorporating a remarkable combination of performance and unique design elements.



F581-ORB

Oil Rubbed Bronze Finish
Bahama Beige™ Blades
with Etched Glass

Sunseeker



Features:

- 14° Blade Pitch
- 5-Blades 60" Sweep
- Galvanized Steel
3½" and 6" Downrods
- Stainless Steel Hardware and
All Weather Blades
- 3-Speed Pull Chain
- Indoor/Outdoor Use
UL Listed for Wet Locations
- UL Wet Location Light Kits
Available
(Sold Separately. Page(s): 241)

F532-BWH

Bone White Finish
Bone White Blades

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
6,783	65	104.19

Lifetime
WARRANTY



The Sunseeker features a 60-inch sweep, stylish transitional design and superb value. These elements make it an ideal choice for enjoying hot summer days outdoors.



F532-BNW

Brushed Nickel Wet Finish
Silver Blades



F532-DRF

Driftwood Finish
Driftwood Blades



F532-ORB

Oil Rubbed Bronze Finish
Oil Rubbed Bronze Blades

Sundowner®



F589-ORB

Oil Rubbed Bronze Finish
Dark Maple Blades

Features:

- 16° Blade Pitch
- 5-Blades 54" Sweep
- Galvanized Steel
3½" and 6" Downrods
- Stainless Steel Hardware and
All Weather Blades
- 3-Speed Pull Chain
- Poly Molded and ABS Components
- Indoor/Outdoor Use
UL Listed for Wet Locations
- UL Wet Location Light Kits
Available
(Sold Separately. Page(s): 241)

Energy Information (Excludes Lights)


Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
6,523	79	82

Lifetime
WARRANTY


LISTED
For Wet Location



Accessory Blades Available. See Page(s): 246



F589-BWH

Bone White Finish
Bone White Blades



F589-DRF

□ Driftwood Finish
Driftwood Blades

Highly recommended for the most challenging environments, the Sundowner® combines superior performance with weatherproof components designed to withstand all outdoor conditions.



F589-MW

□ Mossoro Walnut™ Finish
Mossoro Walnut™ Blades

Sundowner®



F589-HT

Heritage™ Finish
Black Blades

Features:

- 16° Blade Pitch
- 5-Blades 54" Sweep
- Galvanized Steel
3½" and 6" Downrods
- Stainless Steel Hardware and
All Weather Blades
- 3-Speed Pull Chain
- Poly Molded and ABS Components
- Indoor/Outdoor Use
UL Listed for Wet Locations
- UL Wet Location Light Kits
Available
(Sold Separately. Page(s): 241)

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
6,523	79	82

Lifetime
WARRANTY



Accessory Blades Available. See Page(s): 246



F589-WH

White Finish
White Blades



F589-VRT

Vintage Rust™ Finish
Dark Maple Blades



F589-BI/AI

Black Iron with Aged Iron Accents Finish
Black Iron Blades



□ **F571-DRF 52"**

Driftwood Finish
Gray Blades



□ **F571-WH 52"**

White Finish
White Blades



□ **F571-ORB 52"**

Oil Rubbed Bronze Finish
Dark Oak Finish Blades

Sundance™



F572-WH 42"

White Finish
White Blades

Perfect for the porch, patio, gazebo or courtyard, the Sundance™ was designed to withstand all of the elements.

Features:

- 12° Blade Pitch
- 5-Blades 52" or 42" Sweep
- Galvanized Steel
3½" and 6" Downrods
- Stainless Steel Hardware and All Weather Blades
- 3-Speed Pull Chain
- Indoor/Outdoor Use
UL Listed for Wet Locations
- UL Wet Location Light Kits Available
(Sold Separately. Page(s): 241)

F571 Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
5,596	63	88.4

F572 Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
3,428	52	65.64



F572-ORB 42"

Oil Rubbed Bronze Finish
Dark Oak Finish Blades

Lifetime
WARRANTY



For Wet Location




F840-CF

Craftsman™ Finish
Craftsman™ Blades
with Craftsman™ Glass

Features:

- 14° Blade Pitch
- 5-Blades 52" Sweep
- Galvanized Steel
3½" and 6" Downrods
- Stainless Steel Hardware and
All Weather Blades
- Full Function Wall Control System
- Light Kit with Enclosed Glass
Shades
Uses 3-60W Candelabra Bulbs
(Included)
- Indoor/Outdoor Use
UL Listed for Wet Locations
- Cap for Non-Light Use (Included)



F840-CF

Shown with Cap for
Non-Light Use

U.S. Patent(s): D579,097; D579,098; D579,103;
D581,512; D583,044

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
5,374	77.7	69.16



WCS212

Full Function Wall Control System Included
For Details See Page(s): 233

Inspired by the Craftsman architecture of the early 1900s, this fan best defines the spirit of the era. It can be used in both interior and exterior applications.

Lifetime
WARRANTY

WallControl
FULL FUNCTION



For Wet Location





F727-BN/MM

Brushed Nickel Finish
Medium Maple Blades

Value Collection

With the Minka-Aire® Value Collection, one need not sacrifice style and performance for affordability.

Choose from several finishes and light kit options to find the right Minka-Aire® ceiling fan with timeless style and design for the budget-conscious customer.

Rudolph



F727-BN/MM

Brushed Nickel Finish
Medium Maple Blades

Features:

- 14° Blade Pitch
- 3-Blades 52" Sweep
- 3½" and 6" Downrods
- Converts to Electronic Control System
- Universal Light Kit Adaptable (Sold Separately. Page(s): 239)

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
6,665	84.94	78.47



WC116

Wall Control System Included
For Details See Page(s): 233

Lifetime
WARRANTY

Remote
CONTROL
FULL FUNCTION



F727-DK

Distressed Koa Finish
Distressed Koa Blades



F727-BN/SL
Brushed Nickel Finish
Silver Blades

Inspired by a contemporary architect of the 50's, this clean three blade design best exemplifies today's trend in home furnishings. Included is a wall control, cast blade holders, and a 172 x 16mm motor for great air movement.



F727-ORB
Oil Rubbed Bronze Finish
Tobacco Blades

Dyno

with LED Light

LED



LED

F1000-BN

Brushed Nickel Finish
Reversible Medium Maple / Dark Walnut Finish Blades
with Etched Lens
(Shown with Dark Walnut Blades)

Features:

- 12° Blade Pitch
- 5-Blades 52" Sweep
- 3½" and 6" Downrods
- Integrated Light
Uses 17W Dimmable LED
(Included) 3 Year Warranty
- 1,100 Lumens
- 2,700K
- CRI 80
- Hand Held Remote Control System
- Replacement LED Assembly
(Part #6F1000LK01)

U.S. Patent(s): Pending

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
5,295	68.93	76.82



RCS213

Hand Held Remote Control Included
For Details See Page(s): 232

A new addition to our Value Collection, featuring performance and design features at an affordable price. For the first time in our Value offerings, we introduce a fan with an integrated LED* light source. Generous in size, style, adaptability and function, Dyno becomes one of our core fan offerings.

LED

Lifetime WARRANTY

Remote CONTROL



LED

LED

F1000-ORB


Oil Rubbed Bronze Finish
Reversible Medium Maple / Dark Walnut Finish Blades
with Etched Lens
(Shown with Dark Walnut Blades)



F1000-WH

White Finish
White Finish Blades
with Etched Lens

Traditional Mojo



F622-BWH

Bone White Finish
Bone White Blades
with Bone White Glass

The Traditional Mojo is the next generation of our highly successful Mojo series. Traditional accents integrate perfectly for your home.



F622-ORB

Oil Rubbed Bronze Finish
Reversible Medium Maple / Dark Walnut Blades
with Etched White Glass
(Shown with Medium Maple Blades)



F622-ORB/TS

Oil Rubbed Bronze Finish
Reversible Medium Maple / Dark Walnut Blades
with Tea Stain Glass
(Shown with Medium Maple Blades)



F622-PW

Pewter Finish
Reversible Medium Maple / Dark Walnut Blades
with Etched White Glass
(Shown with Dark Walnut Blades)

Features:

- 12° Blade Pitch
- 5-Blades 52" Sweep
- 3½" and 6" Downrods
- 3-Speed Pull Chain
- Low Profile Bowl Light Kit
Uses 3-60W Candelabra Bulbs
(Included)
- Cap for Non-Light Use (Included)
- Solid Cap and Finial Adaptation for
Remote Control Use (Included)

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
5,699	66.1	86.22

Lifetime
WARRANTY

Mojo



F522-ORB/TS

Oil Rubbed Bronze Finish
Reversible Medium Maple / Dark Walnut Blades
with Tea Stain Glass
(Shown with Medium Maple Blades)

Features:

- 12° Blade Pitch
- 5-Blades 52" Sweep
- 3½" and 6" Downrods
- 3-Speed Pull Chain
- Low Profile Light Kit
Uses 3-60W Candelabra Bulbs
(Included)
- Warp Resistant Plywood Blades
- Cap for Non-Light Use (Included)
- Solid Cap and Finial Adaptation Kit
for Remote Control Use (Included)

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
5,295	65.7	81



F522-BN

Brushed Nickel Finish
Reversible Medium Maple / Dark Walnut Blades
with Frosted White Glass
(Shown with Medium Maple Blades)

Lifetime
WARRANTY



F522-WH

White Finish
White Blades
with Frosted White Glass



F522-BWH

Bone White Finish
Bone White Blades
with Frosted White Glass



F522-ORB

Oil Rubbed Bronze Finish
Reversible Medium Maple / Dark Walnut Blades
with Frosted White Glass
(Shown with Medium Maple Blades)

Mojo II



F533-BN

Brushed Nickel Finish
Reversible Medium Maple / Dark Walnut Blades
with Frosted White Glass
(Shown with Dark Walnut Blades)



F533-DK

Distressed Koa Finish
Reversible Medium Maple / Dark Walnut Blades
with Tea Stain Glass
(Shown with Dark Walnut Blades)



F533-WH

White Finish
White Blades
with Frosted White Glass



F533-ORB

Oil Rubbed Bronze Finish
Reversible Medium Maple / Dark Walnut Blades
with Tea Stain Glass
(Shown with Dark Walnut Blades)

The Mojo II is another addition to our Value Collection featuring a wealth of performance and an integrated light source. A great value for low ceiling applications.



F533-BWH

Bone White Finish
Bone White Blades
with Bone White Glass

Features:

- 14° Blade Pitch
- 4-Blades 52" Sweep
- Flush Mount - Ideal for Low Ceilings
Total Hanging Depth 13" with Light
- 3-Speed Pull Chain
- Integrated Downlight
Uses 3-60W Candelabra Bulbs (Included)
- Solid Cap and Finial Adaptation for Remote Control Use (Included)

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
5,138	62.6	82



Hilo



F470-BN

Brushed Nickel Finish
Medium Maple / Dark Walnut Blades
with Frosted White Glass
(Shown with Dark Walnut Blades)

Features:

- 12° Blade Pitch
- 5-Blades 52" Sweep
- 3½" and 6" Downrods
- 3-Speed Pull Chain
- Reversible Warp Resistant Blades
- Bowl Light Kit
Uses 3-40W Candelabra Bulbs
(Included)
- Cap for Non-Light Use (Included)

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
4,828	64.7	74.62

The Hilo's clean lines provide elegance and simplicity suitable for a variety of environments.

Lifetime
WARRANTY



F470-WH

White Finish
White / Medium Maple Blades
with Frosted White Glass
(Shown with White Blades)



F470-ORB

Oil Rubbed Bronze Finish
Medium Maple / Dark Walnut Blades
with Tea Stain Glass
(Shown with Medium Maple)



F510-BS

- Brushed Steel Finish
Silver Blades
with Etched Opal Glass



F510-WH

- White Finish
White Blades
with Etched Opal Glass

Spacesaver



F510-ORB

Oil Rubbed Bronze Finish
Oil Rubbed Bronze Blades
with Tinted Opal Glass

Contemporary styling and superb air circulation for those smaller spaces in your home; perfect for kitchens and food preparation areas, bathrooms, walk-in closets and hallways.

Features:

- 14° Blade Pitch
- 3-Blades 26" Sweep
- Flush Mount - Ideal for Low Ceilings
Total Hanging Depth 10¾"
- 4-Speed Fan
Full Range Dimmer
3-Wire Installation Wall Control
Converts to Electronic Control
- Integrated Halogen Light
Uses 1-50W Mini-Can Halogen Bulb (Included)

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
2,132	30	71.07



WC110-WH

Wall Control System Included
For Details See Page(s): 233


Lifetime
WARRANTY

WallControl

Retro Style Fan

minkaAire®
A Minka Group® Co.

A special series of fans that go where you go. These portable fans offer the same style, quality and value you expect from Minka-Aire® in a compact and portable design. An accent that is reminiscent of times past, our Retro Style Fan is your quiet companion; a stylistic, subtle, tabletop solution for your comfort needs in any room.



F300-ORB
Oil Rubbed Bronze Finish
Oil Rubbed Bronze Blades



F300-BN
Brushed Nickel Finish
Brushed Nickel Blades

Features:

- 4-Blade Turbofan 10" Sweep
- 3 Speeds: 1,250, 1,400 and 1,500 R.P.M.
- Oscillates 70° Side to Side
- Manual Tilt
- Portable (Net Weight 7lbs.)
- 72" Heavy Duty Cord Length
- Steel Construction
- One Year Limited Warranty



F656L-BN/DW

Brushed Nickel Finish
Reversible Medium Maple / Dark Walnut Blades
with Frosted White Glass
(Shown with Dark Walnut Blades)

Economy Collection

Our Economy section offers quality ceiling fans that will not break your budget. This collection of ceiling fans are comprised of quality materials and designed to uphold the Minka-Aire® commitment to excellence.



F588-SP-WH

White Finish
White Blades

Ultra-Max™, by name and performance, is engineered with a 14° blade pitch to provide maximum comfort in even the largest areas. Its clean, traditional styling will be “right at home” in any setting.



F588-SP-BN

Brushed Nickel Finish
Dark Walnut Blades

Ultra-Max™



F588-SP-BCW

Belcaro Walnut™ Finish
Dark Walnut Blades



F588-SP-BWH

Bone White Finish
Bone White Blades

Features:

- 14° Blade Pitch
- 5-Blades 54" Sweep
- 3½" and 6" Downrods
- Full Function Wall Control System and Hand Held Remote Control
- Quick Connect Detachable Switch Cup
- Universal Light Kit Adaptable (Sold Separately. Page(s): 239)

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
6,341	76.4	83



RCS212

Full Function Hand Held Remote Control Included
For Details See Page(s): 232



WCS212

Full Function Wall Control System Included
For Details See Page(s): 233

Lifetime
WARRANTY

WallControl
FULL FUNCTION

Remote
CONTROL
FULL FUNCTION





F569-BS

Brushed Steel Finish
Silver Blades
with Opal Glass

A truly exceptional value! All the benefits of the Supra® 52" packaged with additional bells and whistles including a matching light kit and RCS223 Remote Control System.



F569-ORB

Oil Rubbed Bronze Finish
Medium Maple Blades
with Opal Glass

Supra[®] 52"

with Light Kit



F569-BS/DW

Brushed Steel Finish
Dark Walnut Blades
with Opal Glass



F569-WH

White Finish
White Blades
with Opal Glass



RCS223

Hand Held Remote Control Included
For Details See Page(s): 232

Features:

- 14° Blade Pitch
- 5-Blades 52" Sweep
- 6-Ply Warp Resistant Blades
- 3½" and 6" Downrods
- Hand Held Remote Control System
- Halogen Light Kit
Uses 1-100W Mini-Can Halogen Bulb (Included)

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
5,755	79	72.85

Lifetime
WARRANTY

Remote
CONTROL



The Supra® 52" offers decorative versatility in multiple finishes. It has clean, modern styling and uncompromising quality with superior performance.

F568-KA

Kocoa Finish
Reversible Toned Medium Maple / Medium Maple Blades
(Shown with Toned Medium Maple Blades)

Features:

- 14° Blade Pitch
- 5-Blades 52" Sweep
- 6-Ply Warp Resistant Blades
- 3½" and 6" Downrods
- 3-Speed Pull Chain
- Quick Connect Detachable Switch Cup
- Universal Light Kit Adaptable (Sold Separately. Page(s): 239)

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
5,995.05	75.3	79.62



F568-BWH

Bone White Finish
Bone White Blades



Accessory Blades Available. See Page(s): 246

Supra[®] 52"



F568-SWH

Shell White Finish
Shell White Blades



F568-BS/DW

Brushed Steel Finish
Dark Walnut Blades



□ **F568-WH**

White Finish
White Blades



□ **F568-BCW**

Belcaro Walnut™ Finish
Dark Walnut Blades

Supra[®] 52"



F568-ORB

Oil Rubbed Bronze Finish
Medium Maple Blades



F568-BS

Brushed Steel Finish
Silver Blades

Features:

- 14° Blade Pitch
- 5-Blades 52" Sweep
- 6-Ply Warp Resistant Blades
- 3½" and 6" Downrods
- 3-Speed Pull Chain
- Quick Connect Detachable Switch Cup
- Universal Light Kit Adaptable (Sold Separately. Page(s): 239)

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
5,995.05	75.3	79.62

Lifetime
WARRANTY



Accessory Blades Available. See Page(s): 246



F563-SP

□ Brushed Steel Finish
Silver Blades
with Opal Glass



F563-SP-BS/DW

□ Brushed Steel Finish
Dark Walnut Blades
with Opal Glass

Supra[®] 44"

with Light Kit



F563-SP-ORB

Oil Rubbed Bronze Finish
Medium Maple Blades
with Opal Glass

The Supra[®] 44", model F563-SP is a great economical option, packaged with a light kit to meet every need.



F563-SP-WH

White Finish
White Blades
with Opal Glass

Features:

- 14° Blade Pitch
- 5-Blades 44" Sweep
- 6-Ply Warp Resistant Blades
- 3½" and 6" Downrods
- 3-Speed Pull Chain
- Halogen Light Kit
Uses 1-100W Mini-Can Halogen Bulb (Included)

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
5,272	76	69.37

Lifetime
WARRANTY

Supra[®] 44"



Designed with superior performance and all of the features found in full-size fans made available for mid-size rooms.

F563-BS/DW

Brushed Steel Finish
Dark Walnut Blades

Features:

- 14° Blade Pitch
- 5-Blades 44" Sweep
- 6-Ply Warp Resistant Blades
- 3½" and 6" Downrods
- 3-Speed Pull Chain
- Quick Connect Detachable Switch Cup
- Universal Light Kit Adaptable (Sold Separately. Page(s): 239)

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
5,272	76	69.37

F563-BS

Brushed Steel Finish
Silver Blades



Lifetime
WARRANTY

Accessory Blades Available. See Page(s): 246



F563-ORB

Oil Rubbed Bronze Finish
Medium Maple Blades



F563-WH

White Finish
White Blades

Supra[®] 32"



F562-WH

White Finish
White Blades

Features:

- 22° Blade Pitch
- 6-Blades 32" Sweep
- 6-Ply Warp Resistant Blades
- 3½" and 6" Downrods
- 3-Speed Pull Chain
- Quick Connect Detachable Switch Cup
- Universal Light Kit Adaptable (Sold Separately. Page(s): 239)

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
4,075	66	61.73

Fashion, form and function for the smallest areas are highlighted in the Supra[®] 32". The perfect choice for bathrooms, hallways, entries and walk-in closets.

Lifetime
WARRANTY

Accessory Blades Available. See Page(s): 246



F562-BS

Brushed Steel Finish
Silver Blades



F562-ORB

Oil Rubbed Bronze Finish
Medium Maple Blades

LED



F656L-ORB

Oil Rubbed Bronze Finish
Reversible Medium Maple / Dark Walnut Blades
with Frosted White Glass
(Shown with Dark Walnut Blades)

LED



F656L-WH

White Finish
White Blades
with Frosted White Glass

Contractor Uni-Pack LED

with LED Light

LED

F656L-BN/DW

Brushed Nickel Finish
Reversible Medium Maple / Dark Walnut Blades
with Frosted White Glass
(Shown with Dark Walnut Blades)

Introducing a full feature LED Contractor 52-inch fan. Featuring the incredible 26 watt LED*, 1,647 Lumens, 3,000 Kelvin light source and a 172 x 14mm heavy duty motor.

Features:

- 12° Blade Pitch
- 5-Blades 52" Sweep
- 3½" and 6" Downrod
- 3-Speed Pull Chain
- Low Profile LED Light
Uses 26W LED (Included)
3 Year Warranty
- 1,647 Lumens
- 3,000K
- CRI 82
- Solid Cap and Finial Adaptation for Remote Control Use (Included)

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
5,994	74.6	80.35

Lifetime
WARRANTY

* LED (Light Emitting Diodes)

LED



F556L-BN

Brushed Nickel Finish
Silver Blades
with Etched Lens

Features:

- 12° Blade Pitch
- 5-Blades 52" Sweep
- 3½" and 6" Downrods
- Hand Held Remote Control System
- Integrated LED Light
Uses 17W LED (Included)
3 Year Warranty
- 1,100 Lumens
- 3,000K
- CRI 80
- Replaceable LED Assembly
(Part #6F1000LK01)

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
5,966	66.5	89.71



F556L-BWH

Bone White Finish
Bone White Blades
with Etched Lens



RCS213

Hand Held Remote Control Included
For Details See Page(s): 232

Lifetime
WARRANTY

LED

Contractor LED

with LED Light

LED

F556L-ORB

Oil Rubbed Bronze Finish
Reversible Medium Maple / Dark Walnut Blades
with Etched Lens
(Shown with Medium Maple Blades)

Smart simplicity at its best. This Contractor LED provides greater performance and offers energy efficiency through the use of the latest LED* technology.

F556L-BN/DW

Brushed Nickel Finish
Reversible Medium Maple / Dark Walnut Blades
with Etched Lens
(Shown with Dark Walnut Blades)



F556-BN

Brushed Nickel Finish
Silver Blades



F556-BWH

Bone White Finish
Bone White Blades

Features:

- 12° Blade Pitch
- 5-Blades 52" Sweep
- 3½" and 6" Downrods
- 3-Speed Pull Chain
- Universal Light Kit Adaptable
(Sold Separately. Page(s): 241)

Energy Information

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
5,966	66.5	89.71



Contractor Plus



F556-ORB

Oil Rubbed Bronze Finish
Reversible Medium Maple / Dark Walnut Blades
(Shown with Medium Maple Blades)

Our Contractor Plus fan continues our tradition of offering design and reliability in several finishes.



F556-BN/DW

Brushed Nickel Finish
Reversible Medium Maple / Dark Walnut Blades
(Shown with Dark Walnut Blades)

Contractor Uni-Pack

with 3-Light Kit



F647-BS

Brushed Steel Finish
Dark Walnut Blades
with Etched Glass

Features:

- 12° Blade Pitch
- 4 or 5-Blades 52" Sweep
- 4" Downrod
- 3-Speed Pull Chain
- Integrated Light Kit
Uses 3-60W Candelabra Bulbs
(Included)

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
4,901	62	79.05



F647-ORB

Oil Rubbed Bronze Finish
Medium Maple Blades
with Etched Glass

Lifetime
WARRANTY


Accessory Blades Available. See Page(s): 246



F647-ORB/TS

Oil Rubbed Bronze Finish
Medium Maple Blades
with Tea Stain Glass

Offering affordable performance and reliability with designer finishes, the Contractor fan now comes with an integrated light kit.



F647-WH

White Finish
White Blades
with Etched Glass

Contractor Uni-Pack

with Bowl Light Kit



F648-BS

Brushed Steel Finish
Dark Walnut Blades
with Etched Swirl Glass

Features:

- 12° Blade Pitch
- 4 or 5-Blades 52" Sweep
- 4" Downrod
- 3-Speed Pull Chain
- Bowl Light Kit (Included)
Uses 2-13W Non-Dimmable GU24
Spiral CFL Bulbs (Included)
- Pre-Installed One-Piece Motor
Blade Iron Gasket
- Cap for Non-Light Use (Included)

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
5,408	65	82.69

Our most economical and efficient fan and light combination for the budget-conscious customer, helping to save money and protect the environment through energy efficient products.

Lifetime
WARRANTY





F648-ORB/EX

Oil Rubbed Bronze Finish
Medium Maple Blades
with Excavation Glass



F648-WH

White Finish
White Blades
with Etched Swirl Glass



F648-ORB

Oil Rubbed Bronze Finish
Medium Maple Blades
with Etched Swirl Glass



F548-WH

White Finish
White Blades
with Etched Swirl Glass



F548-ORB

Oil Rubbed Bronze Finish
Medium Maple Blades
with Etched Swirl Glass

Contractor Uni-Pack

with Bowl Light Kit



F548-ORB/EX

Oil Rubbed Bronze Finish
Medium Maple Blades
with Excavation Glass

The most economical and efficient fan and light combination for the secondary rooms in the house.

Features:

- 12° Blade Pitch
- 4 or 5-Blades 52" Sweep
- 4" Downrod
- 3-Speed Pull Chain
- Bowl Light Kit (Included)
Uses 3-60W Candelabra Bulbs (Included)
- Pre-Installed One-Piece Motor Blade Iron Gasket
- Cap for Non-Light Use (Included)

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
4,636	64	73.01

Lifetime
WARRANTY

Accessory Blades Available. See Page(s): 246

www.minkaaire.com

223



F548-BS

Brushed Steel Finish
Silver Blades
with Etched Swirl Glass



F548-BWH

Bone White Finish
Bone white Blades
with Etched Swirl Glass

Contractor Uni-Pack

with Bowl Light Kit



F548-BS/DW

Brushed Steel Finish
Dark Walnut Blades
with Etched Swirl Glass

Features:

- 12° Blade Pitch
- 4 or 5-Blades 52" Sweep
- 4" Downrod
- 3-Speed Pull Chain
- Bowl Light Kit (Included)
Uses 3-60W Candelabra Bulbs (Included)
- Pre-Installed One-Piece Motor Blade Iron Gasket
- Cap for Non-Light Use (Included)

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
4,636	64	73.01

Lifetime
WARRANTY

Accessory Blades Available. See Page(s): 246

www.minkaaire.com

225

Contractor 52"



F547-ORB

Oil Rubbed Bronze Finish
Medium Maple Blades

Features:

- 12° Blade Pitch
- 4 or 5-Blades 52" Sweep
- 4" Downrod
(Uses 3/4" I.D. DR5 Series Downrod)
- 3-Speed Pull Chain
- Quick Connect Detachable Switch Cup
- Pre-Installed One-Piece Motor/
Blade Iron Gasket
- Universal Light Kit Adaptable
(Sold Separately. Page(s): 239)

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
4565	61	74.84

Our Contractor series offers affordable performance and reliability. Designer finishes have been made available to match current trends and demands.



F547-WH

White Finish
White Blades

Lifetime
WARRANTY

Accessory Blades Available. See Page(s): 246



F547-BS/DW

Brushed Steel Finish
Dark Walnut Blades



F547-BWH

Bone White Finish
Bone White Blades



F547-BS

Brushed Steel Finish
Silver Blades



F546-ORB

Oil Rubbed Bronze Finish
Medium Maple Blades



F546-BS

Brushed Steel Finish
Silver Blades

Contractor 42"



F546-BS/DW

Brushed Steel Finish
Dark Walnut Blades

Our Contractor 42" series offers affordable performance and reliability. Designer finishes have been made available to match current trends and demand.



F546-WH

White Finish
White Blades

Features:

- 12° Blade Pitch
- 4 or 5-Blades 42" Sweep
- 4" Downrod
- 3-Speed Pull Chain
- Quick Connect Detachable Switch Cup
- Pre-Installed One-Piece Motor/Blade Iron Gasket
- Universal Light Kit Adaptable (Sold Separately. Page(s): 239)

Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
3,290	47	70.01

Lifetime
WARRANTY

Mesa

minkaAire®
A Minka Group® Co.



F565-WH 52"

White Finish
White Blades

Our close-to-ceiling economy model in two sizes will move air in the tightest places.

Features:

- 12° Blade Pitch
- 5-Blades 52" or 42" Sweep
- Flush Mount 8¾" Overall Ceiling Drop
- 3-Speed Pull Chain
- One-Piece Stamped Body
- Quick Connect Detachable Switch Cup
- Universal Light Kit Adaptable (Sold Separately. Page(s): 239)

F565 Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
5,092	66	78

F566 Energy Information (Excludes Lights)

Airflow CFM	Electricity Used Watts	Airflow Efficiency CFM/Watts
3,291	50	65.82



F566-WH 42"

White Finish
White Blades

Lifetime
WARRANTY

2 1/4" Glass Shades



2018A
 Opal
 4 3/4"Dia. x 4 1/2"H



*** 2548**
 Etched Opal
 5 3/4"Dia. x 4 1/2"H



*** 2549**
 Etched Marble
 5 3/4"Dia. x 4 1/2"H



*** 2560**
 Frosted/Clear
 5"Dia. x 4 3/4"H



2565
 Etched Seeded
 4 3/4"Dia. x 4 3/4"H



*** 2593-1**
 Aged Champagne
 5"Dia. x 5 1/4"H



*** 2593-2**
 Excavation
 5"Dia. x 5 1/4"H



*** 2593-4**
 Venetian Scavo
 5"Dia. x 5 1/4"H



*** 2593-5**
 French Cream
 5"Dia. x 5 1/4"H



2632
 Salon Scavo™
 5"Dia. x 4 3/4"H



2636
 Tuscan Scavo
 5"Dia. x 4 3/4"H



2645
 Linen
 5"Dia. x 5 1/4"H



2646
 Tuscan Scavo
 5"Dia. x 5 1/4"H



2652
 Etched Marble
 5"Dia. x 4 3/4"H



4099
 4" Opal Glass Shade
 8 1/2"Dia. x 5 1/2"H

* An Original Minka Group® Design

Control Systems



RCS212 - 256 Bit

RCS212 Full Function Hand Held AireControl® Remote System

- Three Speed Fan Control in Forward and Reverse
- On/Off Plus Full Range Light Dimmer with Independent Up/Downlight Control
- Includes One (1) Hand Held Remote Control, Wall Holster
- Wireless Remote Operation
- Operates at Distance of 20-40' Distance; Depends on Quality/Materials Used in Construction of Room/Building Fan is Hung In
- Can be Used in Conjunction with WCS212 Wall Mount AireControl®
- 12 Volt Battery Included

U.S. Patent(s): D533,514; D551,008; 8,253,272



RCS213 - 256 Bit

RCS213 Hand Held AireControl® Remote System

- Three Speed Fan Control
- On/Off Plus Full Range Light Dimmer
- Includes One (1) Hand Held Remote Control, Wall Holster
- Wireless Remote Operation
- Operates at Distance of 20-40' Distance; Depends on Quality/Materials Used in Construction of Room/Building Fan is Hung In
- Can be Used in Conjunction with WCS223 Wall AireControl®
- 12 Volt Battery Included

U.S. Patent(s): D533,514; D551,008; 8,253,272



RCS223 - 256 Bit

RCS223 Hand Held AireControl® Remote System

- Three Speed Fan Control
- On/Off Plus Full Range Light Dimmer
- Includes One (1) Hand Held Remote Control, Wall Holster and Canopy Mounted Receiver
- Wireless Remote Operation
- Operates at Distance of 20-40' Distance; Depends on Quality/Materials Used in Construction of Room/Building Fan is Hung In
- Can be Used in Conjunction with WCS213 Wall AireControl®
- 12 Volt Battery Included

U.S. Patent(s): D533,514; D551,008; 8,253,272



RC400 / RC500 / RC600

RC400 AireControl® Remote System

- For F726, F787L, F823, F828, F838L, F887, F888 and F889 Fans Only
- Six Speed Fan Control in Forward and Reverse
- On/Off Plus Full Range Light Dimmer
- Includes One (1) Hand Held Remote Control, Wall Holster
- Wireless Remote Operation
- Operates at Distance of 23' Distance; Depends on Quality/Materials Used in Construction of Room/Building Fan is Hung In

U.S. Patent(s): D533,514; D551,008

RC500 AireControl® Remote System

- For F737 and F853 Fans Only
- Same Features as RC400 AireControl® System

U.S. Patent(s): D533,514; D551,008

RC600 AireControl® Remote System

- For F617L, F745, F899L and F905 Fans Only
- Same Features as RC400 AireControl® System

U.S. Patent(s): D533,514; D551,008



Full Function Hand Held Remote Control



An ultra-thin design exclusive to Minka-Aire®, the remote enables the user with one finger to control all functions of Minka-Aire® ceiling fans.

AireControl® by Minka-Aire® controls all functions: reverse, uplight (where applicable), fan light, speed control, as well as off-on (RCS212 and WCS212)

RCS213, RCS223, WCS213 and WCS223 controls do not include the reverse function.

Included is a holster if you want to wall mount the control for your convenience.

Please Note:

256 Bit remote systems are not compatible with 32 Bit remote systems.

WC105-WH Speed Control

- Four Speed Fan Control
- 2-Wire Installation

WC115 Speed Control

- For F624 Fans Only
- Four Speed Fan Control
- 2-Wire Installation

WC106-WH Speed Control

- Four Speed Fan Control
- Full Range Dimmer
- 3-Wire Installation

WC110 Speed Control

- For F510 Fans Only
- Same Features as WC106-WH

WC116 Speed Control

- For F727 Fans Only
- Same Features as WC106-WH

WCS212 Full Function AireControl®

- Same Features as RC212 Hand Held
- Includes Ivory, White and Brown Finish Inner/Outer Plates

U.S. Patent(s): D533,514; 8,253,272

WCS213 AireControl®

- Same Features as RCS213 Hand Held
- Includes Ivory, White and Brown Finish Inner/Outer Plates

U.S. Patent(s): D533,514; 8,253,272



WC105-WH White / WC115



WC106-WH White / WC110 / WC116



WCS212 - 256 Bit



WCS213 - 256 Bit

WCS223 AireControl®

- Same Features as RC223 Hand Held
- Includes Ivory, White and Brown Finish Inner/Outer Plates

U.S. Patent(s): D533,514; 8,253,272



WCS223 - 256 Bit

WC400 AireControl®

- Same Features as RC400 Hand Held
- For F726, F787L, F823, F828, F838L, F887, F888 and F889 Fans Only
- Includes Ivory, White and Brown Finish Inner/Outer Plates

U.S. Patent(s): D533,514

WC500 AireControl®

- Same Features as R500 Hand Held
- For F737 and F853 Fans Only
- Includes Ivory, White and Brown Finish Inner/Outer Plates

U.S. Patent(s): D533,514

WC600 AireControl®

- Same Features as R600 Hand Held
- For F617L, F745, F899L and F905 Fans Only
- Includes Ivory, White and Brown Finish Inner/Outer Plates

U.S. Patent(s): D533,514



WC400 / WC500 / WC600

Please Note:

256 Bit remote systems are not compatible with 32 Bit remote systems.

Control Systems - Compatibility Chart

FAN MODEL	FAN NAME	PAGE	RCS212	RCS213	RCS223	WC105-WH	WC106-WH	WCS212	WCS213	WCS223
F302	Gyrette™	196	Incl.					•		
F304L	Cage Free Gyro™	130	•					Incl.		
F306L	Elemental Gyro™	131	•					Incl.		
F402	Gyro™ Wet	135	•					Incl.		
F476/F574	Concept™ II Wet 52"	151	•					Incl.		
F477/F577	Concept™ I Wet 58"	148	•					Incl.		
F502	Traditional Gyro™	129	•					Incl.		
F510	Spacesaver	194				Wall Control Included WC110				
F513	New Era	96	Incl.					•		
F514	Zen	92	Incl.					•		
F516	Concept™ I 44"	74	Incl.					•		
F517	Concept™ I 52"	74	Incl.					•		
F518	Concept™ II 44"	78	Incl.					•		
F519	Concept™ II 52"	76	Incl.					•		
F521	Aluma	54			•		Incl.			•
F522	Mojo	188			•		•			•
F523	Aluma Wet	162		Incl.						
F524	Roto	44			•	Incl.				•
F528	San Francisco®	66		•		•			Incl.	
F529	San Francisco®	66		•			•		Incl.	
F531	Flyte®	64		•			•		Incl.	
F532	Sunseeker	172				•	•			
F533	Mojo II	268		•	•		•		•	•
F539	Great Room Traditional	118	•					Incl.		
F544	Calais™	127		Incl.			•		•	
F546	Contractor 42"	228			•	•	•			•
F547	Contractor 52"	226			•	•	•			•
F548	Contractor Uni-Pack	222			•		•			•
F556	Contractor Plus	216			•		•			•
F556L	Contractor LED	214		Incl.					•	
F562	Supra® 32"	210			•	•	•			•
F563	Supra® 44"	208			•	•	•			•
F563	Supra® 44" -SP	206			•		•			•
F565	Mesa™ 52"	230				•	•			
F566	Mesa™ 42"	230				•	•			
F568	Supra® 52"	202			•	•	•			•
F569	Supra® 52"	200		•	Incl.		•		•	
F571	Sundance™ 52"	178				•	•			
F572	Sundance™ 42"	179				•	•			
F580	Shangri-La®	169					•			
F581	Gauguin™	170	•					Incl.		
F582	Rainman™	166		•			•		Incl.	
F588	Ultra-Max™	198	Incl.					Incl.		
F589	Sundowner®	174				•	•			
F593	Traditional Concept™ 44"	82, 156	•					Incl.		
F594	Traditional Concept™ 52"	80, 154	•					Incl.		
F596	Cirque™	86	•					Incl.		
F598	Airus™	94	•					Incl.		
F601	Acero™	88	•					Incl.		
F602	Gyro™	134	•					Incl.		

FAN MODEL	FAN NAME	PAGE	RCS212	RCS213	RCS223	WC105-WH	WC106-WH	WCS212	WCS213	WCS223
F603	Como™	90	•					Incl.		
F614	Timeless	104			•	•	•			•
F617L	Raptor	6				Special Remote Included RC600, Compatible with WC600				
F620	Bolo™	116		Incl.			•		•	
F622	Traditional Mojo	186			•		•			•
F624	Roto XL	146				Wall Control Included WC115				
F647	Contractor Uni-Pack	218			•		•			•
F648	Contractor Uni-Pack	220			•					•
F656L	Contractor Uni-Pack LED	212			Compatible with WCS213 & RCS213 - must use Receiver L001021500S					
F659	Classica	124			•	•	•			•
F672	Iconic™	102	Incl.					•		
F681	Groton	144	Incl.							
F688	Kola	110			•	•	•			•
F689	Kola-XL	269	Incl.					•		
F695	Kafé	114		•	•	•				•
F696	Kafé-XL	112	Incl.					•		
F701	Delano®	98		•			•		Incl.	
F702	Volterra™	126		•			•		Incl.	
F705	Napoli™	122	•					Incl.		
F711	Delano® II	100	•					Incl.		
F715	Napoli™ II	123	•					Incl.		
F726	Spectre	38				Special Remote Included RC400, Compatible with WC400				
F727	Rudolph	182				Wall Control Included WC116				
F733	Gilera	68	•					Incl.		
F734	Strata	164		Incl.						
F737	Moda	72				Special Remote Included RC500, Compatible with WC500				
F738	Pancake	14	Incl.					•		
F745	Sabot	46				Special Remote Included RC600, Compatible with WC600				
F753	Java	52, 160		Incl.						
F753L	Java LED	50, 158		Incl.						
F759	Classica Gallery Edition	124		Incl.					•	
F787	Simple	42, 142				Special Remote Included RC400, Compatible with WC400				
F802	Vintage Gyro™	132	•					Incl.		
F803	Artemis™	8	•					Incl.		
F812	Lineage™	121	•					Incl.		
F820	Santa Lucia™	120	•					Incl.		
F823	Wing	56				Special Remote Included RC400, Compatible with WC400				
F824	Uchiwa	84	•					Incl.		
F828	Symbio	48				Special Remote Included RC400, Compatible with WC400				
F833	Kewl	62			•	Incl.				•
F838L	Force	4				Special Remote Included RC400, Compatible with WC400				
F840	Craftsman™	180	•					Incl.		
F843	Wave	60		Incl.					•	
F844	Light Wave	58		Incl.					•	
F853	Aviation	34				Special Remote Included RC500, Compatible with WC500				
F887	Xtreme	22				Special Remote Included RC400, Compatible with WC400				
F888	Slipstream	30, 140				Special Remote Included RC400, Compatible with WC400				
F889	Slipstream XXL	26, 138				Special Remote Included RC400, Compatible with WC400				
F899L	Ninety-Nine	16				Special Remote Included RC600, Compatible with WC600				
F900	Cristafano™	128	•					Incl.		
F905	Artemis™ XL5	32				Special Remote Included RC600, Compatible with WC600				
F1000	Dyno	184		Incl.					•	

Hanging Systems



FINISH	ABDD	BCW	BG	BI	BK	BN	BN/MG	BNW	BS	BWH	CC	CF	CPBR	CT	DBB	DKG	DRB	DRFF	FB	GL	GM	HT	IBR	IO	KA	LN
--------	------	-----	----	----	----	----	-------	-----	----	-----	----	----	------	----	-----	-----	-----	------	----	----	----	----	-----	----	----	----

DR5 SERIES DOWNROD ARE 3/4" I.D.

	ABDD	BCW	BG	BI	BK	BN	BN/MG	BNW	BS	BWH	CC	CF	CPBR	CT	DBB	DKG	DRB	DRFF	FB	GL	GM	HT	IBR	IO	KA	LN	
DR500-COUPLER	•**	•	•	•	•	•	-	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
DR512	•	•	•	•	•	•	-	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
DR518	•	•	•	•	•	•	-	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
DR524	•	•	•	•	•	•	-	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
DR536	•	•	•	•	•	•	-	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
DR548	•	•	•	•	•	•	-	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
DR560	•	•	•	•	•	•	-	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
DR572	•	•	•	•	•	•	-	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•

PRE-WIRED DOWNBRIDGE™ KIT (FOR USE WITH F528 AND F529 ONLY)

	ABDD	BCW	BG	BI	BK	BN	BN/MG	BNW	BS	BWH	CC	CF	CPBR	CT	DBB	DKG	DRB	DRFF	FB	GL	GM	HT	IBR	IO	KA	LN	
DK06-6"	-	-	-	-	-	-	-	-	•	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
DK24-24"	-	-	-	-	-	-	-	-	•	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
DK36-36"	-	-	-	-	-	-	-	-	•	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
DK48-48"	-	-	-	-	-	-	-	-	•	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
DK60-60"	-	-	-	-	-	-	-	-	•	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
DK72-72"	-	-	-	-	-	-	-	-	•	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-

DOWNLINK™ KIT (FOR USE WITH F531 ONLY)

	ABDD	BCW	BG	BI	BK	BN	BN/MG	BNW	BS	BWH	CC	CF	CPBR	CT	DBB	DKG	DRB	DRFF	FB	GL	GM	HT	IBR	IO	KA	LN	
DL06-6"	-	-	-	-	-	•	•	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
DL15-15"	-	-	-	-	-	•	•	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
DL27-27"	-	-	-	-	-	•	•	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
DL39-39"	-	-	-	-	-	•	•	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
DL51-51"	-	-	-	-	-	•	•	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
DL63-63"	-	-	-	-	-	•	•	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
DL75-75"	-	-	-	-	-	•	•	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-

MINKA-AIRE® 45° SLOPE CEILING ADAPTER KITS (SCA)


* A245 3/4" I.D.	•**	•	•	•	•	•	-	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
A180	-	•	-	•	•	•	-	•	•	•	•	-	•	•	•	•	•	•	•	•	•	-	•	•	-	•	•
*** A581	-	-	•	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-

Minka-Aire® offers a full selection of downrods in 59 finishes and 8 lengths to complement any Minka-Aire® ceiling fan.

* A245 3/4" I.D. is also available in PR (Primer) finish.

** For F524-ABD, only.

*** For F581, only.



FINISH	MCG	MG	MP	MW	ODK	ORB	PBL	PI	PN	PW	RD	RRB	RW	SI	SDBK	SL	STW/GOW	SWH	TSP	VB	VP	VRT	WA	WH/44	WHF
--------	-----	----	----	----	-----	-----	-----	----	----	----	----	-----	----	----	------	----	---------	-----	-----	----	----	-----	----	-------	-----

DR5 SERIES DOWNROD ARE 3/4" I.D.

DR500-COUPLER	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
DR512	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
DR518	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
DR524	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
DR536	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
DR548	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
DR560	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
DR572	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•

PRE-WIRED DOWNBRIDGE™ KIT (FOR USE WITH F528 AND F529 ONLY)

DK06-6"	-	-	-	-	-	•	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
DK24-24"	-	-	-	-	-	•	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
DK36-36"	-	-	-	-	-	•	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
DK48-48"	-	-	-	-	-	•	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
DK60-60"	-	-	-	-	-	•	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
DK72-72"	-	-	-	-	-	•	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-

DOWNLINK™ KIT (FOR USE WITH F531 ONLY)

DL06-6"	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	•	-
DL15-15"	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	•	-
DL27-27"	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	•	-
DL39-39"	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	•	-
DL51-51"	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	•	-
DL63-63"	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	•	-
DL75-75"	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	•	-

MINKA-AIRE® 45° SLOPE CEILING ADAPTER KITS (SCA)

* A245 3/4" I.D.	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•	•
A180	•	•	•	•	•	•	•	•	•	-	-	•	-	-	•	•	•	-	•	•	-	•	-	•	•	
*** A581	-	-	-	-	-	•	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	•	

All component parts and hardware supplied with your Minka-Aire® ceiling fan have been designed and engineered to assure proper and safe installation of your new ceiling fan. Substituting parts or hardware, such as, but not limited to the hanger ball and the hanger bracket, not supplied with your ceiling fan by Minka-Aire®, will void the Minka-Aire® Warranty.

Hanging Systems



Low Ceiling Adapter A180

For use on:
F513, F514, F522, F546, F547, F548, F556, F562, F563, F568, F569, F588, F589, F596, F601, F603, F614, F620, F622, F647, F648, F659, F688, F689, F695, F696, F759, F824, F905

Low Ceiling Adapter A581

For use on:
F581



A581-BG

A581-ORB

A581-WHF

Pre-Wired Downbridge™ Kit (for use on F528 and F529 only)



DK36

Downlink™ Kit (for use on F531 only)



DL39

Downbridge™ Kit Maximum length is 72"

(Size and Finish: See Page(s): 66)

Note: It is not possible to join Downbridge™ or Downlink™ kits together for hanging fans in excess of maximum kit lengths.

Downlink™ Kit Maximum length is 72"

(Size and Finish: See Page(s): 64)



Downrod Coupler DR500 (3/4" I.D.)

For those occasions when you need to hang your ceiling fan on a longer than 72" downrod, simply use one of our downrod couplers (DR500) available in finishes to match all our fans and downrods. The coupler enables you to couple our 3/4" downrods together and hang fans on total downrod lengths of up to 144".




Slope Ceiling Adapter Kit (SCA) A245-BN (3/4" I.D.)

U.S. Patent(s): 7,510,160

Minka-Aire® 45° Slope Ceiling Adapter Kit (SCA)

Minka-Aire® SCA Kit was designed to meet the needs of the home building industry as demand increases for higher, more steeply angled ceilings. Minka-Aire® A245 SCA is used with 3/4" I.D. DR5 Series Downrod.

Sloped Ceiling Application with standard hanging systems for slopes up to a maximum of 29°



The above kit as shown includes the mounting bracket, the angled ball assembly and locking pin. For fans that weigh in excess of 35lbs, simply use the hanging bracket that comes with the fan in the box (75lbs rating standard) and the kit's angled ball assembly and locking pin. (Fan model numbers F528, F529 and F531 do not apply because of their unique Downbridge™ hanging systems)

Sloped Ceiling Installation

Minka-Aire® ceiling fans equipped with universal hanging systems may be hung from standard or vaulted ceilings up to 21° pitch.

When ordering SCA specify finish to match your needs.

Finishes Available:

ABR, BCW, BG, BI, BK, BN, BNW, BS, BWH, CC, CF, CH, CPBR, CT, DBB, DKG, DRB, DRF, FB, FLP, GL, HT, IBR, IO, KA, LN, MCG, MG, MP, MW, ORB, PBL, PI, PN, PR, PW, RD, RRB, SI, SL, SLV, STW/GOW, SWH, TSP, VB, VP, VRT, WH, WHF

(PR - Primer finish ready for painting to match your ceiling)

F738 Fan Only



Internal Threaded Downrod (3/4" I.D.)

	ASL	DK	ORB	WHF
DR1512	•	•	•	•
DR1518	•	•	•	•
DR1524	•	•	•	•
DR1536	•	•	•	•
DR1548	•	•	•	•
DR1560	•	•	•	•
DR1572	•	•	•	•

Universal Light Kits



K9500

Two Light
Belcaro Walnut™
60W Candelabra Base (Included)
11 ¼" Dia. x 6 ½"H



K9515-1

Three Light
Frosted White
40W Candelabra Base (Included)
12 ¼" Dia. x 2 ½"H
Includes Brushed Nickel & White Caps



K9515-2

Three Light
Tea Stain
40W Candelabra Base (Included)
12 ¼" Dia. x 2 ½"H
Includes Dark Brushed Bronze & Oil Rubbed Bronze Caps



K9525-1

Three Light
Frosted White
40W Candelabra Base (Included)
12 ¼" Dia. x 2 ½"H
Includes Brushed Nickel & White Caps



K9525-2

Three Light
Tea Stain
40W Candelabra Base (Included)
12 ¼" Dia. x 2 ½"H
Includes Dark Brushed Bronze & Oil Rubbed Bronze Caps



* K9548

Three Light
Etched Swirl
60W Candelabra Base (Included)
12" Dia. x 5"H



K9380-1

Two Light
French Scavo
13W GU24 Spiral CFL Base (Included)
11 ½" Dia. x 5 ½"H



K9380-2

Two Light
Excavation
13W GU24 Spiral CFL Base (Included)
11 ½" Dia. x 5 ½"H



Please Note: All Light Kits include Chain with Decorative Fob. (Not shown)

* Additional Cap Finishes Available

Universal Light Kits



*** K9369-L**

Three Light
Etched Swirl
60W Candelabra Base (Included)
13 1/4\"/>



K9372-1

Three Light
Caspian™
60W Candelabra Base (Included)
13 1/4\"/>



K9372-2

Three Light
Excavation
60W Candelabra Base (Included)
13 1/4\"/>



K9372-3

Three Light
Parchment
60W Candelabra Base (Included)
13 1/4\"/>



K9372-4

Three Light
Venetian Scavo
60W Candelabra Base (Included)
13 1/4\"/>



K9372-5

Three Light
Alabaster Dust™
60W Candelabra Base (Included)
13 1/4\"/>



*** K9363-L**

Three Light
Etched Marble
60W Candelabra Base (Included)
13 1/4\"/>



*** K9376-1**

Three Light
Caspian™
60W Candelabra Base (Included)
16\"/>



*** K9376-2**

Three Light
Excavation
60W Candelabra Base (Included)
16\"/>

Please Note: All Light Kits Include Chain with Decorative Fob. (Not Shown)



*** Additional Cap Finishes Available**

- | | | | |
|-----------|---------------------|---------------|-------------------------------------|
| AC100 | Swirled Glass | AC100-MCG | Mottled Copper with Gold Highlights |
| AC100-BCW | Belcaro Walnut™ | AC100-ORB | Oil Rubbed Bronze |
| AC100-BS | Brushed Steel | AC100-PBL | Provencal Blanc |
| AC100-BWH | Bone White | AC100-PI | Patina Iron |
| AC100-CT | Cattera Bronze™ | AC100-PW | Pewter |
| AC100-DBB | Dark Brushed Bronze | AC100-STW/GOW | Sterling Walnut™/Golden Walnut |
| AC100-EX | Excavation | AC100-SWH | Shell White |
| AC100-FB | French Beige | AC100-VRT | Vintage Rust™ |
| AC100-KA | Koccoa | | |



K9373-L-BS



K9373-L-ORB



K9373-L-WH

K9373

One Light Opal Glass
50W Mini-Can Xenon (Included)
9 1/2" Dia. x 5 1/4"H
For 30"/32" Sweep Fans



K9374-L-BS



K9374-L-WH

K9374

One Light Opal Glass
50W Mini-Can Xenon (Included)
10 1/2" Dia. x 5 1/4"H
For 40"/44" Sweep Fans



K9375-L-BS



K9375-L-BWH

K9375

One Light Opal Glass
50W Mini-Can Xenon (Included)
11 1/2" Dia. x 5 3/4"H
For 50"/56" Sweep Fans



K9375-L-ORB



K9375-L-WH

Please Note: All Light Kits Include Chain with Decorative Fob. (Not Shown)

Wet Location

K9401

Two Light Opal Glass
13W GU24 Spiral CFL Bulbs (Included)
10 1/2" Dia. x 5 1/2"H



K9401-L-BWH



K9401-L-DRF



K9401-L-HT



K9401-L-MW



K9401-L-ORB



K9401-L-VRT



K9401-L-WH

K9402

One Light Opal Glass
60W Candelabra Base (Included)
7 3/4" Dia. x 8 1/2"H



K9402-L-ORB



K9402-L-44

Finish Codes

BCW	Belcaro Walnut™	ORB	Oil Rubbed Bronze
BS	Brushed Steel	SWH	Shell White
BWH	Bone White	VRT	Vintage Rust™
HT	Heritage™	WH/44	White
MW	Mossoro Walnut™		

Universal Light Kits

K37


Four Light
40W Candelabra Base (Included)
2 1/4" Side Shade
13"Dia. x 6 1/2"H




K37-L-BCW

K1

Four Light
40W Candelabra Base (Included)
2 1/4" Side Fitter
11 3/4"Dia. x 3"H




K1-L-BCW



K1-L-BS



K1-L-ORB



K1-L-44

K1099

One Light
Opal Glass
60W Candelabra Base (Included)
8 1/2"Dia. x 6 3/4"H



K1099-1-L-44



K9365-L-44 (Low Profile)

Three Light
Etched Marble
60W Candelabra Base (Included)
12 1/2"Dia. x 4 1/2"H



GC900 SET

Optional Crystal Set
Available Only for the F900 Fan



Finish Codes

ABR	Antique Bronze	BS	Brushed Steel	SWH	Shell White
BCW	Belcaro Walnut™	ORB	Oil Rubbed Bronze	WVH/44	White

Please Note: All Light Kits Include Chain with Decorative Fob. (Not Shown)



K33-L-BS



K33-L-DBB



K33-L-FB



K33-L-MCG



K33-L-ORB



K33-L-PI




K33-L-44

K33

Three Light
60W Candelabra Base (Included)
2 1/4" Side Shade
6 1/4"Dia. x 3 1/2"H



K35-BN



K35-BS



K35-CC



K35-DBB



K35-FB



K35-KA



K35-MCG



K35-ORB



K35-PBL



K35-PI



K35-PW



K35-SWH



K35-VP



K35-44

K35

Three Light
13W Spiral Medium Base
(Included)
2 1/4" Side Shade
7 1/4"Dia. x 3 1/2"H

Finish Codes

BN	Brushed Nickel	KA	Kocca	PW	Pewter
BS	Brushed Steel	MCG	Mottled Copper w/Gold	SWH	Shell White
CC	Cognac	ORB	Oil Rubbed Bronze	VP	Vineyard Patina
DBB	Dark Brushed Bronze	PBL	Provencal Blanc	WH/44	White
FB	French Beige	PI	Patina Iron		

Please Note: All Light Kits Include Chain with Decorative Fab. (Not Shown)

Universal Light Kits

K34


Four Light
13W Spiral Medium Base
(Included)
2 1/4" Side Shade
11 3/4"Dia. x 2 3/4"H




K34-BN



K34-BCW



K34-BS



K34-CC




K34-DBB



K34-KA



K34-MCG




K34-ORB



K34-PI



K34-PW



K34-SWH



K34-44

Custom LED Light Kits

K9787L

LED Light
15W LED (Incl.)
5"Dia. x 1 1/2"H
1,300 Lumens
3,000 Kelvin
CRI 80

Compatible with the
F787 Simple Fans Only

Pull Chains Not Applicable



K9787L-ORB



K9787L-SL



K9787L-WHF

Finish Codes

BN	Brushed Nickel	MCG	Mottled Copper w/Gold	SWH	Shell White
BS	Brushed Steel	ORB	Oil Rubbed Bronze	VP	Vineyard Patina
CC	Cognac	PBL	Provencal Blanc	WH/44	White
DBB	Dark Brushed Bronze	PI	Patina Iron	WHF	Flat White
FB	French Beige	PW	Pewter		
KA	Kocoa	SL	Silver		

Please Note: All Light Kits Include Chain
with Decorative Fob. (Not Shown)



Custom LED Light Kits



K9838L-DK



K9838L-SL



K9838L-WH

K9838L

LED Light
15W LED (Incl.)
6½" Dia. x 1¾" H
1,300 Lumens
3,000 Kelvin
CRI 80

Compatible with the
F838L Force Fans Only

Pull Chains Not Applicable

Custom Light Kits



K9614-DBB



K9614-FB



K9614-MCG

K9614

Three Light
60W Candelabra Base (Included)
2¼" Side Shade
8½" Dia. x 3¼" H

Compatible with the
F614 Timeless Fans Only



K9614-PI



K9614-PW



K9659-BCW



K9659-DRF



K9659-FB

K9659

Three Light
60W Candelabra Base (Included)
2¼" Side Shade
7½" Dia. x 3½" H

Compatible with the
F659 Classica Fans Only



K9659-MCG



K9659-PBL



K9659-PI

Finish Codes


BCW	Belcaro Walnut™	FB	French Beige	PI	Patina Iron
DBB	Dark Brushed Bronze	MCG	Mottled Copper w/Gold	PW	Pewter
DK	Distressed Koa	ORB	Oil Rubbed Bronze	SL	Silver
DRF	Driftwood	PBL	Provencal Blanc	WH	White

Please Note: All Light Kits Include Chain with Decorative Fob. (Not Shown)


Accessory Fan Blades




CW
Cherry Wood




DC
Dark Cherry



DM
Dark Maple



DW
Dark Walnut




LC
Light Cherry



LM
Light Maple



ML
Reversible
Medium Oak



MM
Medium Maple

Fan Blade Compatibility Chart

Model	Fan Name	CW	DC	DM	DW	LC	LM	ML	MM	MO
F516	Concept™ I	N/A	N/A	FB216-DM	FB216-DW	N/A	N/A	N/A	N/A	N/A
F517	Concept™ I	N/A	N/A	FB217-DM	FB217-DW	N/A	N/A	N/A	N/A	N/A
F518	Concept™ II	N/A	N/A	FB216-DM	FB216-DW	N/A	N/A	N/A	N/A	N/A
F519	Concept™ II	N/A	N/A	FB217-DM	FB217-DW	N/A	N/A	N/A	N/A	N/A
F528	San Francisco®	FB106-CW	N/A	N/A	N/A	N/A	N/A	N/A	FB106-MM	N/A
F529	San Francisco®	FB106-CW	N/A	N/A	N/A	N/A	N/A	N/A	FB106-MM	N/A
F547	Contractor	N/A	N/A	FB103S-DM	FB103S-DW	FB103S-LC	FB103S-LM	FB103S-ML	FB103S-MM	N/A
F548	Contractor Uni-Pack	N/A	N/A	FB103S-DM	FB103S-DW	FB103S-LC	FB103S-LM	FB103S-ML	FB103S-MM	N/A
F562	Supra® 32"	N/A	FB422-DC	FB422-DM	FB422-DW	FB422-LC	FB422-LM	N/A	FB422-MM	N/A
F563	Supra® 44"	N/A	FB423-DC	FB423-DM	FB423-DW	FB423-LC	FB423-LM	N/A	FB423-MM	N/A
F568	Supra® 52"	N/A	FB424-DC	FB424-DM	FB424-DW	FB424-LC	FB424-LM	N/A	FB424-MM	N/A
F588	Ultra-Max™ 54"	FB107T-CW	N/A	N/A	FB107T-DW	FB107T-LC	N/A	N/A	FB107T-MM	N/A
F589	Sundowner®	N/A	N/A	FB107P-DM	FB107P-DW	N/A	N/A	N/A	FB107P-MM	N/A
F596	Cirque™	Optional Blades Sets are the FB196-RYB (Multi-colored, Red, Yellow, Blue) and the FB196-MG (Mahogany Finish)								
F647	Contractor Uni-Pack	N/A	N/A	FB103S-DM	FB103S-DW	FB103S-LC	FB103S-LM	FB103S-ML	FB103S-MM	N/A



Fan Blade Compatibility Chart

Model	Fan Name	NM	NP	NW	ORB	RW	SL	SWH	WO	WP	
F516	Concept™ I	N/A	N/A	N/A	FB216-ORB	N/A	N/A	N/A	N/A	N/A	
F517	Concept™ I	N/A	N/A	N/A	FB217-ORB	N/A	N/A	N/A	N/A	N/A	
F518	Concept™ II	N/A	N/A	N/A	FB216-ORB	N/A	N/A	N/A	N/A	N/A	
F519	Concept™ II	N/A	N/A	N/A	FB217-ORB	N/A	N/A	N/A	N/A	N/A	
F528	San Francisco®	N/A	N/A	N/A	N/A	N/A	FB106-SL	N/A	N/A	N/A	
F529	San Francisco®	N/A	N/A	N/A	N/A	N/A	FB106-SL	N/A	N/A	N/A	
F547	Contractor	FB103S-NM	N/A	FB103S-NW	N/A	FB103S-RW	FB103S-SL	FB103S-SWH	FB103S-WO	FB103S-WP	
F548	Contractor Uni-Pack	FB103S-NM	N/A	FB103S-NW	N/A	FB103S-RW	FB103S-SL	FB103S-SWH	FB103S-WO	FB103S-WP	
F562	Supra® 32"	N/A	N/A	FB422-NW	N/A	N/A	FB422-SL	N/A	FB422-WO	FB422-WP	
F563	Supra® 44"	N/A	N/A	FB423-NW	N/A	N/A	FB423-SL	N/A	FB423-WO	FB423-WP	
F568	Supra® 52"	N/A	N/A	FB424-NW	N/A	N/A	FB424-SL	FB424-SWH	FB424-WO	FB424-WP	
F588	Ultra-Max™ 54"	N/A	FB107T-NP	FB107T-NW	N/A	FB107T-RW	N/A	N/A	FB107T-WO	FB107T-WP	
F589	Sundowner®	N/A	N/A	N/A	N/A	N/A	N/A	FB107P-SWH	N/A	N/A	
F596	Cirque™		Optional Blades Sets are the FB196-RYB (Multi-colored, Red, Yellow, Blue) and the FB196-MG (Mahogany Finish)								
F647	Contractor Uni-Pack	FB103S-NM	N/A	FB103S-NW	N/A	FB103S-RW	FB103S-SL	FB103S-SWH	FB103S-WO	FB103S-WP	

Finishes



AB
Antique Brass



ABD / ABDD
Brushed Aluminum



BCW
Belcaro Walnut™



BG
Bahama Beige™



BI/AI
Black Iron/
Aged Iron Accents



BK
Black



BN
Brushed Nickel
(Plated)



BNW
Brushed Nickel Wet
(Plated)



BS
Brushed Steel



BWH
Bone White



CC
Cognac



CF
Craftsman™



CH
Chrome
(Plated)



CPBR
Copper Bronze



CT
Cattera Bronze™



DBB
Dark Brushed Bronze



DK / ODK
Distressed Koa



DKG
Distressed Koa with
Gold Highlights



DRB
Dark Restoration Bronze™



DRF / DRFF
Driftwood



FB
French Beige



GBZ
Golden Bronze



GM
Gun Metal



GL
Galvanized



HT
Heritage™



IBR
Illuminati Bronze™



IO
Iron Oxide



KA
Kocoa



LN
Liquid Nickel
(Plated)



MBK
Matte Black



MCG
Mottled Copper
with Gold Highlights



MG
Mahogany



MP
Maple



MW
Mossoro Walnut™



ORB
Oil Rubbed Bronze



ORG
Orange



PBL
Provencal Blanc



PI
Patina Iron



PN
Polished Nickel
(Plated)



PW
Pewter



RD
Red



RRB
Restoration Bronze™



RW
Rosewood



SDBK
Sand Black



SI
Smoked Iron



SL
Silver



STW
Sterling Walnut™



SWH
Shell White



TB
Toned Brass
(Plated)



TSP
Tuscan Patina™



VB
Volterra Bronze™



VP
Vineyard Patina



VRT
Vintage Rust™



WH
White



WHF
Flat White

Hand-painted finishes and components made from natural material may reflect variations in color and texture. These are not imperfections and enhance the unique appearance of each and every Minka-Aire® fixture. Specifications are subject to change at any time.

Bulb Reference



Watts: 10W / 20W
XENON JCX 12V
G4 BI-PIN BASE

Frosted
JX4-20 (20W)
Clear
JX4C-10 (10W)
JX4C-20 (20W)




Watts: 35W / 50W
XENON JCX 12V
G6.35 BI-PIN BASE

Frosted
JX6-35 (35W)
JX6-50 (50W)



Watts: 25W / 35W / 40W / 60W / 75W
G9 XENON 120V
G9 BASE

Frosted
JX9-025 (25W)
JX9-035 (35W)
JX9-040 (45W)
JX9-060 (60W)
JX9-075 (75W)
Clear
JX9C-025 (25W)
JX9C-040 (40W)



Watts: 20W / 50W
XENON 120V
DC (BAYONET)

JXB15-20 (20W)
JXB15-50 (50W)




Watts: 75W
XENON 120V
E12 (CANDELABRA) BASE

Frosted
JDXF-12-075 (75W)



Watts: 50W / 75W / 100W
MINI-CAN XENON 120V
E11 (CANDELABRA) BASE

Frosted
JDX-050 (50W)
JDX-75 (75W)



Watts: 50W / 75W / 100W
MINI-CAN HALOGEN 120V
E11 (CANDELABRA) BASE

Frosted
JD-50 (50W)
JD-75 (75W)
JD-100 (100W)
Clear
JDC-50 (50W)
JDC-75 (75W)
JDC-100 (100W)



Watts: 50W
JDD XENON 120V
E12 (CANDELABRA) BASE

Frosted
JDX2F-050 (50W)
Clear
JDX2-050 (50W)



Watts: 100W / 150W
78MM 120V DOUBLE ENDED
HALOGEN (J-TYPE)
R7S BASE

J8-100 (100W)
JB-150 (150W)



Watts: 8W DC / 10W AC / 11W AC / 14W AC
LED MODULE

L-18-MD590 (8W)
L-AC10-MODULE (10W)
L-AC10-MD770 (11W)
L-AC14-MD950 (14W)



Watts: 50W
PAR16 HALOGEN
E26 (MEDIUM) BASE

PAR16-50 (50W)



Watts: 35W / 50W
HALOGEN MR16 120V
GU10 BASE

JGU-035 (35W)
JGU-50 (50W)



Watts: 20W / 35W / 50W
HALOGEN MR16
GX5.3 BI-PIN BASE

Frosted
JMR16-20 (20W 120V)
JMR16-35 (35W 120V)
JMR16-50/120V (50W 120V)
Clear
JMR16-C-20 (20W 12V)
JMR16-C-35 (35W 12V)
JMR16-C-50 (50W 12V)



Watts: 13W / 26W
SPIRAL CFL
E26 (MEDIUM) BASE

FLB-13S (13W)



Watts: 13W / 26W
SPIRAL CFL
GU24 BASE

FLB-13M (13W)
FLB-26M (26W)



Watts: 18W / 26W
SQUAT SPIRAL CFL
GU24 BASE

FLS-18M (18W)
FLS-26M (26W)



Watts: 40W
FERRO
E26 (MEDIUM) BASE

E26-FW1910-40W (40W)



Watts: 40W / 60W / 100W
T10 120V
E26 (MEDIUM) BASE

Frosted
JT10-060F (60W)
Clear
JT10-040C (40W)
JT10-060C (60W)
JT10-100C (100W)



Watts: 27W
FULL 24 CFL
GX10q-4 BASE

JT4-27 (27W)




Watts: 13W
4-PIN (PL-C)
G24q-1 BASE

FLT-13Q (13W)



Watts: 27W
CFL
GX10q-4 BASE

JT2-27 (27W)



Watts: 32W
FC12T9 T9 CIRCULUME
G10Q

FLC-22 (22W)
FLC-32 (32W)
FLC-40 (40W)



Watts: 8W / 13W
FLUORESCENT
T5 G13 BI-PIN BASE

Ballast: BLST08-T5
JTS-8
JTS-13



Watts: 7W
C7 CFL
E12 (CANDELABRA) BASE

FLB-07C (7W)



Watts: 75W
MR16
E17 BASE

JDR-75 (75W)



Watts: 40W / 60W
B10.5
E12 (CANDELABRA) BASE

E12 (CANDELABRA) BASE



Watts: 15W
C7
E12 (CANDELABRA) BASE

ECCC-15 (15W)



Watts: 60W
BR30
E26 (MEDIUM) BASE



Watts: 40W / 60W
A15
E26 (MEDIUM) BASE



Watts: 40W / 60W / 75W / 100W
A19
E26 (MEDIUM) BASE



Watts: 150W
A21 (3-WAY)
E26 (MEDIUM) BASE



Watts: 25W / 40W / 60W
G16 1/2
E12 (CANDELABRA) BASE



WATTS: 60W / 100W
G25
E26 (MEDIUM) BASE



Watts: 60W / 100W
G30
E26 (MEDIUM) BASE



Watts: 40W / 60W / 100W
G40
E26 (MEDIUM) BASE

Index

ACCESSORIES

AC100240
AC100-BCW240
AC100-BS240
AC100-BWH240
AC100-CT240
AC100-DBB240
AC100-EX240
AC100-FB240
AC100-KA240
AC100-MCG240
AC100-ORB240
AC100-PBL240
AC100-PI240
AC100-PW240
AC100-STW/GOW . . .240
AC100-SWH240
AC100-VRT240
CM7022-STW122
CM7022-TSP122
CM7038-STW122
CM8222-IBR120
GC900 SET242

ACCESSORY BLADES

FB103S-DM246
FB103S-DW246
FB103S-LC246
FB103S-LM246
FB103S-ML246
FB103S-MM246
FB103S-NM247

FB103S-NW247
FB103S-RW247
FB103S-SL247
FB103S-SWH247
FB103S-WO247
FB103S-WP247
FB106-CW246
FB106-MM246
FB106-SL247
FB107P-DM246
FB107P-DW246
FB107P-MM246
FB107P-SWH247
FB107T-CW246
FB107T-DW246
FB107T-LC246
FB107T-MM246
FB107T-NP247
FB107T-NW247
FB107T-RW247
FB107T-WO247
FB107T-WP247
FB196-MG . 86, 246, 247
FB196-RYB . 87, 246, 247
FB216-DM246
FB216-DW246
FB216-ORB247
FB217-DM246
FB217-DW246
FB217-ORB247
FB422-DC246
FB422-DM246

FB422-DW246
FB422-LC246
FB422-LM246
FB422-MM246
FB422-NW247
FB422-SL247
FB422-WO247
FB422-WP247
FB423-DC246
FB423-DM246
FB423-DW246
FB423-LC246
FB423-LM246
FB423-MM246
FB423-NW247
FB423-SL247
FB423-WO247
FB423-WP247
FB424-DC246
FB424-DM246
FB424-DW246
FB424-LC246
FB424-LM246
FB424-MM246
FB424-NW247
FB424-SL247
FB424-SWH247
FB424-WO247
FB424-WP247

CEILING FANS

F300-BN196

F300-ORB196
F302-BN136
F302-RRB136
F304L-BN/SL130
F304L-ORB/MM130
F306L-BS/SL131
F306L-ORB/MM131
F402-BNW135, 168
F402-ORB135, 168
F470-BN192
F470-ORB193
F470-WH193
F474-ORB152
F474-WH152
F476-ORB151
F476-WH151
F477-BNW149
F477-ORB148
F477-WH148
F502-BCW129
F502-PBL129
F510-BS194
F510-ORB195
F510-WH194
F513-BN96
F513-KA97
F513-ORB96
F513-WH97
F514-BN92
F514-ORB92
F514-WH93
F516-BN75

F516-ORB	74	F529-L-BS/CH	67	F548-ORB/EX	223	F569-BS/DW	201
F516-PN	75	F529-L-ORB	66	F548-WH	222	F569-ORB	200
F516-WH	74	F531-L-BN	64	F556-BN	216	F569-WH	201
F517-BN	75	F531-L-BN/MG	65	F556-BN/DW	217	F571-DRF	178
F517-ORB	74	F531-L-WH	64	F556-BWH	216	F571-ORB	178
F517-PN	75	F532-BNW	173	F556L-BN	214	F571-WH	178
F517-WH	74	F532-BWH	172	F556L-BN/DW	215	F572-ORB	179
F518-BN	78	F532-DRF	173	F556L-BWH	214	F572-WH	179
F518-ORB	79	F532-ORB	173	F556L-ORB	215	F574-BNW	153
F518-PN	79	F533-BN	190	F556-ORB	217	F577-BNW	150
F518-WH	78	F533-BWH	191	F562-BS	211	F580-VR/BB	169
F519-BN	76	F533-DK	190	F562-ORB	211	F581-BG	170
F519-MG	77	F533-ORB	191	F562-WH	210	F581-ORB	171
F519-ORB	76	F533-WH	190	F563-BS	208	F581-WHF	171
F519-PN	76	F539-BCW	118	F563-BS/DW	208	F582-BNW	137, 166
F519-WH	77	F539-BN	119	F563-ORB	209	F582-GL	167
F521-ABD	54	F539-ORB	119	F563-SP	206	F582-ORB	166
F521-ORB	55	F544-BCW	127	F563-SP-BS/DW	206	F588-SP-BCW	199
F521-WHF	55	F544-GBZ	127	F563-SP-ORB	207	F588-SP-BN	198
F522-BN	188	F546-BS	228	F563-SP-WH	207	F588-SP-BWH	199
F522-BWH	189	F546-BS/DW	229	F563-WH	209	F588-SP-WH	198
F522-ORB	189	F546-ORB	228	F565-WH	230	F589-BI/AI	177
F522-ORB/TS	188	F546-WH	229	F566-WH	230	F589-BWH	174
F522-WH	189	F547-BS	227	F568-BCW	204	F589-DRF	175
F523-ABD	162	F547-BS/DW	227	F568-BS	205	F589-HT	176
F523-ORB	162	F547-BWH	227	F568-BS/DW	203	F589-MW	175
F523-WHF	163	F547-ORB	226	F568-BWH	202	F589-ORB	174
F524-ABD	44	F547-WH	226	F568-KA	202	F589-VRT	177
F524-DK	45	F548-BS	224	F568-ORB	205	F589-WH	176
F524-ORB	45	F548-BS/DW	225	F568-SWH	203	F593-ORB	83, 157
F524-WHF	45	F548-BWH	224	F568-WH	204	F593-PW	82, 156
F528-L-BS/CH	66	F548-ORB	222	F569-BS	200	F593-WH	83, 157

Index

F594-ORB80, 154
F594-PW81, 155
F594-WH81, 155
F596-BN 86, 87
F596-PN/TL. 87
F598-BN 95
F598-ORB 94
F598-WH 95
F601-BS/BN 88
F601-BS/MG 88
F601-ORB 89
F601-PN 89
F602-BN/CH134
F602-RRB134
F603-BN 91
F603-ORB 90
F603-WH 90
F614-DBB104
F614-FB106
F614-MCG105
F614-ORB107
F614-PI.105
F614-PW106
F617L-BN 6
F617L-GM 6
F617L-ORB/AB 7
F620-BCW117
F620-BN116
F620-DBB117
F620-ORB116
F622-BWH186
F622-ORB186

F622-ORB/TS.187
F622-PW187
F624-ABD147
F624-ORB146
F624-WHF147
F647-BS218
F647-ORB218
F647-ORB/TS.219
F647-WH219
F648-BS220
F648-ORB221
F648-ORB/EX.221
F648-WH221
F656L-BN/DW . 197, 213
F656L-ORB212
F656L-WH212
F659-BCW125
F659-DRF125
F659-FB125
F659-PBL.124
F659-PI.125
F672-MBK/BN103
F672-ORB102
F672-ORB/AB. . . .103
F672-WH/BN102
F681-BNW144
F681-ORB145
F681-PN145
F681-SDBK/WS. . . .144
F681-WA/PW144
F688-DBB111
F688-KA110

F688-PW110
F688-WH111
F689-DBB109
F689-KA108
F689-PW108
F689-WH109
F695-CC115
F695-KA114
F695-VP115
F695-WH115
F696-CC112
F696-KA112
F696-VP113
F696-WH113
F701-DRB 98
F701-DRF 99
F701-KA 99
F701-PN 99
F701-PW 98
F702-BCW126
F702-VB126
F705-STW122
F711-DRB100
F711-PN101
F711-PW101
F715-STW123
F715-TSP.123
F726-BN/ORG. 39
F726-BN/SL 38
F726-ORB/AB. 40
F726-ORB/BN. 41
F726-WHF/BN . . 39, 40

F727-BN/MM . . 181, 182
F727-BN/SL 183
F727-DK 182
F727-ORB 183
F733-BK/RW 68
F733-BS/BN 70
F733-PN 70
F733-SL 69
F733-WH 71
F734-GL 165
F734-ORB 164
F734-SI 165
F737-BN 72
F737-ORB 73
F737-WH. 72
F738-DK 15
F738-ORB 14
F738-SL 14
F738-WHF 15
F745-BN 47
F745-DK 46
F745-ORB 47
F753-BNW 52, 161
F753-KA 52, 160
F753L-BNW 50, 158
F753L-KA 51, 159
F753L-PN 51, 159
F753L-WHF. 50, 158
F753-PN 53
F753-WHF 53, 161
F759-PBL 124
F787-ORB 42, 142

F787-SL	43, 143	F833-WH	62	F899L-DK	20	2549	231
F787-WHF	43, 143	F838L-DK	5	F899L-ORB	18	2560	231
F802-BN/CH	133	F838L-SL	4	F900-BCW	128	2565	231
F802-KA	132	F838L-WH	4	F905-DK	33	2593-1	231
F802-ORB	133	F840-CF	180	F905-SL	32	2593-2	231
F803-BK	13	F843-DK	61	F905-WH	33	2593-4	231
F803-CPBR	11	F843-SL	60	F1000-BN	184	2593-5	231
F803-DK	8	F843-WH	61	F1000-ORB	185	2632	231
F803-LN	8	F844-DK	58	F1000-WH	185	2636	231
F803-MG	9	F844-SL	59			2645	231
F803-MP	13	F844-WH	59	CONTROL SYSTEMS		2646	231
F803-RD	10	F853-BN/DK	34	RC400	232	2652	231
F803-SL	11	F853-BN/MM	37	RC500	232	4099	231
F803-TL	12	F853-BN/SL	37	RC600	232		
F803-WH	12	F853-RW	35	RCS212	232	HANGING SYSTEMS	
F812-IO	121	F853-WH	36	RCS213	232	A180	236, 237, 238
F820-CT	120	F887-72-BN	22	RCS223	232	A245	236, 237
F820-IBR	120	F887-72-ORB	24	WC105-WH	233	A245-BN	238
F823-DK	56	F887-80-BN	22	WC106-WH	233	A581	236, 237
F823-SL	57	F887-80-ORB	24	WC110	233	A581-BG	170, 238
F823-WH	57	F887-88-BN	22	WC115	233	A581-ORB	238
F824-BK/CH	85	F887-88-ORB	24	WC116	233	A581-WHF	238
F824-ORB/TB	84	F887-96-BN	22	WC400	233	DK06	236, 237
F824-WH	85	F887-96-ORB	24	WC500	233	DK24	236, 237
F828-BN	48	F888-BNW	30, 140	WC600	233	DK36	236, 237, 238
F828-BN/DW	49	F888-DK	31, 141	WCS212	233	DK48	236, 237
F828-BN/WH	49	F888-ORB	31, 141	WCS213	233	DK60	236, 237
F828-ORB	48	F888-WHF	31, 141	WCS223	233	DK72	236, 237
F828-WHF	48	F889-BNW	26, 139			DL06	236, 237
F833-BK	63	F889-ORB	28, 138	GLASS SHADES		DL15	236, 237
F833-RD	62	F889-SI	29, 138	2018A	231	DL27	236, 237
F833-SL	63	F899L-BN/SL	16, 21	2548	231	DL39	236, 237, 238

Index

DL51	236, 237
DL63	236, 237
DL75	236, 237
DR500	236, 237, 238
DR512	236, 237
DR518	236, 237
DR524	236, 237
DR536	236, 237
DR548	236, 237
DR560	236, 237
DR572	236, 237
DR1512	238
DR1518	238
DR1524	238
DR1536	238
DR1548	238
DR1560	238
DR1572	238

LIGHT KITS - CUSTOM

K9614-DBB	245
K9614-FB	245
K9614-MCG	245
K9614-PI	245
K9614-PW	245
K9659-BCW	245
K9659-DRF	245
K9659-FB	245
K9659-MCG	245
K9659-PBL	245
K9659-PI	245

LIGHT KITS - CUSTOM LED


K9787L-ORB	244
K9787L-SL	43, 143, 244
K9787L-WHF	43, 143, 244
K9838L-DK	245
K9838L-SL	245
K9838L-WH	245

LIGHT KITS - UNIVERSAL

K1-L-44	242
K1-L-BCW	242
K1-L-BS	242
K1-L-ORB	242
K33-L-44	243
K33-L-BS	243
K33-L-DBB	243
K33-L-FB	243
K33-L-MCG	243
K33-L-ORB	243
K33-L-PI	243
K34-44	244
K34-BCW	244
K34-BN	244
K34-BS	244
K34-CC	244
K34-DBB	244
K34-KA	244
K34-MCG	244
K34-ORB	244
K34-PI	244
K34-PW	244
K34-SWH	244

K35-44	243
K35-BN	243
K35-BS	243
K35-CC	243
K35-DBB	243
K35-FB	243
K35-KA	243
K35-MCG	243
K35-ORB	243
K35-PBL	243
K35-PI	243
K35-PW	243
K35-SWH	243
K35-VP	243
K37-L-BCW	242
K1099-1-L-44	242
K9363-L	240
K9365-L-44	242
K9369-L	240
K9372-1	240
K9372-2	240
K9372-3	240
K9372-4	240
K9372-5	240
K9373-L-BS	241
K9373-L-ORB	241
K9373-L-WH	241
K9374-L-BS	241
K9374-L-WH	241
K9375-L-BS	241
K9375-L-BWH	241
K9375-L-ORB	241

K9375-L-WH	241
K9376-1	240
K9376-2	240
K9380-1	239
K9380-2	239
K9401-L-BWH	241
K9401-L-DRF	241
K9401-L-HT	241
K9401-L-MW	241
K9401-L-ORB	241
K9401-L-VRT	241
K9401-L-WH	241
K9402-L-44	241
K9402-L-ORB	241
K9500	239
K9515-1	239
K9515-2	239
K9525-1	239
K9525-2	239
K9548	239



Acero™
F601
Pages 88 - 89



Airus™
F598
Pages 94 - 95



Aluma
F521
Pages 54 - 55



Aluma Wet
F523
Pages 162 - 163



Artemis™
F803
Pages 8 - 13



Artemis™ XL5
F905
Pages 32 - 33



• **Aviation**
F853
Pages 34 - 37



Bolo™
F620
Pages 116 - 117



• **Cage Free Gyro™**
F304L
Page 130



Calais™
F544
Page 127



Cirque™
F596
Pages 86 - 87



• **Classica**
F659
Pages 124 - 125

Fan Styles



Classica - Gallery Edition
F759
Page 124



Como™
F603
Pages 90 - 91



Concept™ I 44"
F516
Pages 74 - 75



Concept™ I 52"
F517
Pages 74 - 75



Concept™ I Wet 52"
F476/F577
Pages 150 - 151



Concept™ I Wet 58"
F477
Pages 148 - 149



Concept™ II 44"
F518
Pages 78 - 79



Concept™ II 52"
F519
Pages 76 - 77



Concept™ II Wet 52"
F474/F574
Pages 152 - 153



Contractor 42"
F546
Pages 228 - 229



Contractor 52"
F547
Pages 226 - 227



Contractor LED
F556L
Pages 214 - 215



• **Contractor Plus**
F556
Pages 216 - 217



Contractor Uni-Pack
F548
Pages 222 - 225



Contractor Uni-Pack
F647
Pages 218 - 219



• **Contractor Uni-Pack**
F648
Pages 220 - 221



• • **Contractor Uni-Pack LED**
F656L
Pages 212 - 213



Craftsman™
F840
Page 180



Cristafano™
F900
Page 128



Delano®
F701
Pages 98 - 99



Delano® II
F711
Pages 100 - 101



• **Dyno**
F1000
Pages 184 - 185



• • **Elemental Gyro™**
F306L
Page 131




Flyte®
F531
Pages 64 - 65

Fan Styles



● Force
F838L
Pages 4 - 5



Gauguin™
F581
Pages 170 - 171



Gilera
F733
Pages 68 - 71



Great Room Traditional
F539
Pages 118 - 119



● Groton
F681
Pages 144 - 145



Gyrette™
F302
Page 136



Gyro™
F602
Page 134



Gyro™ Wet
F402
Pages 135, 168



Hilo
F470
Pages 192 - 193



Iconic™
F672
Pages 102 - 103



Java
F753
Pages 52 - 53, 160 - 161



● ● Java LED
F753L
Pages 50 - 51, 158 - 159



• **Kafé**
F695
Pages 114 - 115



• **Kafé-XL**
F696
Pages 112 - 113




• **Kewl**
F833
Pages 62 - 63



• **Kola**
F688
Pages 110 - 111



• **Kola-XL**
F689
Pages 108 - 109



• **Light Wave**
F844
Pages 58 - 59



Lineage™
F812
Page 121



Mesa™
F565/F566
Page 230



Moda
F737
Pages 72 - 73



Mojo
F522
Pages 188 - 189



Mojo II
F533
Pages 190 - 191



Napoli™
F705
Page 122

Fan Styles



Napoli™ II
F715
Page 123



New Era
F513
Pages 96 - 97



• **Ninety-Nine**
F899L
Pages 16 - 21



• **Pancake**
F738
Pages 14 - 15



Rainman™
F582
Pages 166 - 167



• **Raptor**
F617L
Pages 6 - 7



Retro Style Fan
F300
Page 196



• **Roto**
F524
Pages 44 - 45




• **Roto XL**
F624
Pages 146 - 147



• **Rudolph**
F727
Pages 182 - 183



• **Sabot**
F745
Pages 46 - 47



San Francisco®
F528/F529
Pages 66 - 67



Santa Lucia™
F820
Page 120




Shangri-La®
F580
Page 169



• **Simple**
F787
Pages 42 - 43, 142 - 143



Slipstream
F888
Pages 30 - 31, 140 - 141



• **Slipstream XXL**
F889
Pages 26 - 29, 138 - 139



Spacesaver
F510
Pages 194 - 195



• **Spectre**
F726
Pages 38 - 41



Strata
F734
Pages 164 - 165



• **Sundance™**
F571/F572
Pages 178 - 179



• **Sundowner®**
F589
Pages 174 - 177



• **Sunseeker**
F532
Pages 172 - 173



Supra® 32"
F562
Pages 210 - 211

Fan Styles



Supra® 44"
F563
Pages 208 - 209



Supra® 44" -SP
F563-SP
Pages 206 - 207



• **Supra® 52"**
F568
Pages 202 - 205



Supra® 52" -SP
F569
Pages 200 - 201



• **Symbio**
F828
Pages 48 - 49



• **Timeless**
F614
Pages 104 - 107



Traditional Concept™ 44"
F593
Pages 82 - 83, 156 - 157



Traditional Concept™ 52"
F594
Pages 80 - 81, 154 - 155



Traditional Gyro™
F502
Page 129

Fan Styles



Traditional Mojo
F622
Pages 186 - 187



Uchiwa
F824
Pages 84 - 85



• Ultra-Max™
F588
Pages 198 - 199



Vintage Gyro™
F802
Pages 132 - 133



Volterra™
F702
Page 126



• Wave
F843
Pages 60 - 61



• Wing
F823
Pages 56 - 57



Xtreme
F887
Pages 22 - 25



• Zen
F514
Pages 92 - 93

Terms and Conditions

TERMS – Cash Net 30 Days. Any other terms, regardless of documents submitted by customer, must have written pre-approval from The Minka Group® credit department. A service charge of 1½% per month, but not exceeding any lawful rate, may be charged on all delinquent balances.

PRICE – Prices are subject to change without notice. "Distributor Net" pricing is extended only to authorized Minka-Aire® dealers. Special price quotations are valid for 60 days, unless otherwise indicated.

ORDERS – Purchase orders must include product item number, quantity, price and 'ship to' address.

MINIMUM ORDER – A \$10.00 service charge will be assessed on orders under \$100.00

CREDIT – All orders must be approved by Minka's credit department prior to shipment. Placing an order does not constitute the opening of a new account. Accounts on Credit Hold will not have credits processed for returned goods, cooperative advertising, incentive programs or special promotions, until they are in good credit standing with all Minka® divisions.

FREIGHT – Freight deduction is allowed on orders exceeding \$1,250.00 shipping to the 48 contiguous United States. Freight deduction is also allowed on combined orders (excluding Metropolitan®) totaling \$2000.00. The Freight Allowance policy does not cover accessorial charges which may include, but are not limited, to the following: inside delivery charges, lift gate charges, notification fees, residential delivery fees, re-consignment fees, special construction site delivery charges, or island delivery fees. Deduction will only be permitted if the invoice is paid in full within terms. **FREIGHT DEDUCTIONS ARE NOT ALLOWED IF INVOICE IS PAID OUT OF TERMS.** We reserve the right to select the freight carrier for all shipments. Title passes to consignee once shipment is signed for by carrier. Drop shipments are subject to a \$15.00 service charge.

PRIORITY SHIPMENTS – All orders requiring priority (same day) shipping, limited to a maximum of 50 cartons, including will call orders, will incur a \$20.00 service charge for every 5 cartons. To allow time for processing, the order must be received by Minka® no later than 11:00 A.M., in your respective time zone.

CLAIMS – In the event of loss or damage in transit, **DO NOT REFUSE TO ACCEPT SHIPMENT.** Note shortage or damage on the carrier's delivery receipt and file all claims with the carrier. Rights to recover repayment for claims are relinquished by failure to note shortages and damage on the delivery receipt. Order entry and shipping errors must be reported to Minka's customer care department within 10 days after receiving the shipment.

RETURN OF MERCHANDISE – GOODS MUST BE RETURNED with written authorization and must include an authorization number. Returns without authorization will be refused. Not complying with routing instructions will result in charge-backs. All returns are subject to freight charges and a 25% restocking charge, except for product determined to be defective in material and workmanship by Minka®. Authorized, non-defective returns must be in original factory-sealed cartons. Custom or special order items are not returnable.

SPECIFICATIONS – Minka® reserves the right to change product specifications without prior notice.

PRICING – A Unilateral Minimum Resale Price (UMRP) Policy is in effect for certain Minka-Aire® products. All conditions of the UMRP policy must be adhered to. For detailed information contact your Minka-Aire® representative.

WARRANTY - The Minka-Aire® warranty is for one (1) year from the date of purchase from an authorized Minka-Aire® dealer. This warranty is only valid to the original purchaser or user against all defects in material and workmanship (light bulbs excluded) for one (1) full year. Additionally, Minka-Aire® warrants the motor only for the lifetime of the Minka-Aire® ceiling fan (excluding wall controls and electrical components), to the original purchaser or user. Minka-Aire® fans featuring an LED light kit have a limited Power Supply warranty (Module, PC Board Diodes and Drivers) for three (3) years. **THE WARRANTY IS VOID:** a) with the use of any non-Minka-Aire® electrical devices, e.g., wall controls or electrical dimmer switches, etc., b) once the original purchaser or user ceases to own the fan or the fan is moved from its original point of installation, c) with the use of any hanger bracket (non-Minka-Aire® or non-fan specific) other than the hanger bracket supplied & installed with this specific fan, d) installed in an environment other than its intended use (Indoor fans installed outdoors or in a covered outdoor patio area, or subjected to environmental conditions: salt air, humidity, direct sun exposure, etc.). Outdoor finishes are specifically excluded from the terms of this warranty since they are subject to environmental and maintenance damages beyond our control.

WARRANTY SERVICE INFORMATION - To obtain warranty service during the warranty period, the purchaser should return the fan with the sales receipt to the original place of purchase. The authorized Minka-Aire® dealer, at its sole discretion, will either repair or replace the fan after verifying the legitimacy of the warranty claim. Replacement is subject to availability of the same model. If the model is unavailable it will be replaced by one of equal value. This is a limited warranty; the original purchaser or user is responsible for the cost of removal and reinstallation of repaired or replacement product.

To obtain the name of the Minka-Aire® authorized dealer nearest you, call the Minka-Aire® customer care department at 1-800-307-3267, or contact Minka-Aire® through www.minkagroup.net and fill out the "Submit a Question" form to answer any questions or if you require assistance.

Fan warranty registration can either be mailed as addressed on the warranty card or may be submitted directly online at www.minkagroup.net by clicking on the "Warranty Registration" tab at the top of the page and providing the required information.

GENERAL CONDITIONS – Minka-Aire® may terminate its business relationship with any dealer that fails to maintain adequate stock of Minka-Aire® product. Further, Minka-Aire® may cease selling product to any dealer that sells or distributes to an unauthorized dealer for resale purposes. **TRANSHIPMENT** of products is prohibited to any and all lighting showrooms or other unspecified distribution channel.

Minka Group® reserves the right to select its Authorized Dealers in each division (*) and their channels of distribution for Minka Group® products.

(*) Ambience® by Minka-Lavery®; George Kovacs®; Metropolitan® Lighting Fixture Company; Minka-Aire®; Minka-Lavery®; The Great Outdoors® by Minka-Lavery®

Notes

Fan Specifications

		Page Number	Blade Sweep	No. of Blades	Blade Pitch	Motor Size (m/m)	RPM (Hi/Low)	Warranty	Light Kit	Downrods 3/4" I.D.	Downrods 1/2" I.D.	Lead Wire	Dimensions A	Dimensions B	Hanging Weight (lbs)
F300	Retro Style	196	10"	3	14°	70 x 70	1253/1525	One Year	N/A	N/A	N/A	72"	N/A	N/A	6
F302	Gyrette™	136	36"	8	14°	82 x 25	1470/800	Limited Lifetime	N/A	4 1/2"	N/A	54"	13 3/4"	20"	19
F304L	Cage Free Gyro™	130	37"	6	23°	70 x 16	1470/800	Limited Lifetime	Integrated	3 1/2" & 6"	N/A	80"	19 3/4"	15 1/4"	19
F306L	Elemental Gyro™	131	42"	6	23°	70 x 16	1470/800	Limited Lifetime	Integrated	3 1/2" & 6"	N/A	80"	20 1/2"	15 1/2"	19
F402	Gyro™ Wet	135	42"	6	20°	82 x 25	1350/720	Limited Lifetime	Integrated	3 1/2" & 6"	N/A	80"	17"	15 1/4"	30
F470	Hilo	192	52"	5	12°	153 x 17	173/69	Limited Lifetime	N/A	3 1/2" & 6"	N/A	80"	16"	9 1/2"	18
F474	Concept™ II Wet 52"	152	52"	3	14°	188 x 20	170/92	Limited Lifetime	Integrated	N/A	N/A	8"	12"	8 1/2"	26
F476	Concept™ I Wet 52"	151	52"	3	14°	188 x 20	168/93	Limited Lifetime	Integrated	3 1/2" & 6"	N/A	80"	18"	14 1/2"	25
F477	Concept™ I Wet 58"	148	58"	3	14°	188 x 22	158/68	Limited Lifetime	Integrated	3 1/2" & 6"	N/A	80"	15 3/4"	11 3/4"	27
F502	Traditional Gyro™	129	42"	6	20°	80 x 25	1350/720	Limited Lifetime	Integrated	3 1/2" & 12"	N/A	80"	17"	16 1/2"	40
F510	Spacesaver	194	26"	3	14°	153 x 12	300/274	Limited Lifetime	Integrated	N/A	N/A	8"	11"	7 1/4"	12
F513	New Era	96	52"	4	14°	172 x 16	199/67	Limited Lifetime	Adaptable	3 1/2" & 6"	N/A	80"	13"	10 1/4"	18
F514	Zen	92	52"	4	14°	172 x 16	209/67	Limited Lifetime	Integrated	3 1/2" & 6"	N/A	80"	16"	10 1/4"	20
F516	Concept™ I 44"	74	44"	3	14°	153 x 15	189/91	Limited Lifetime	Integrated	3 1/2" & 6"	N/A	80"	15	11 3/4"	22
F517	Concept™ I 52"	74	52"	3	14°	172 x 20	183/70	Limited Lifetime	Integrated	3 1/2" & 6"	N/A	80"	15"	11 3/4"	25
F518	Concept™ II 44"	78	44"	3	14°	153 x 15	181/79	Limited Lifetime	Integrated	N/A	N/A	8"	11 1/2"	8 1/4"	24
F519	Concept™ II 52"	76	52"	3	14°	172 x 20	172/66	Limited Lifetime	Integrated	N/A	N/A	8"	11 1/2"	8 1/4"	27
F521	Aluma	54	52"	4	12°	153 x 15	187/100	Limited Lifetime	Integrated	3 1/2" & 6"	N/A	80"	13 1/4"	9 3/4"	17
F522	Mojo	188	52"	5	12°	153 x 15	162/60	Limited Lifetime	Included	3 1/2" & 6"	N/A	80"	14 1/2"	9"	18
F523	Aluma Wet	162	52"	4	12°	153 x 20	166/73	Limited Lifetime	Integrated	3 1/2" & 6"	N/A	80"	14"	10 3/4"	19
F524	Roto	44	52"	3	22°	153 x 15	210/112	Limited Lifetime	N/A	3 1/2" & 6"	N/A	80"	9 1/4"	7"	11
F528	San Francisco®	66	56"	3	13°	172 x 17	189/68	Limited Lifetime	N/A	N/A	12" DB	6"	14 1/2"	11 1/2"	19
F529	San Francisco®	66	56"	3	13°	172 x 17	189/68	Limited Lifetime	Integrated	N/A	12" DB	6"	17 1/2"	11 1/2"	22
F531	Flyte®	64	56"	3	14°	188 x 25	178/82	Limited Lifetime	Integrated	N/A	9" DL	80"	17 3/4"	16 1/4"	27
F532	Sunseeker	172	60"	5	14°	188 x 25	135/50	Limited Lifetime	Integrated	3 1/2" & 6"	N/A	80"	14"	12 1/4"	28
F533	Mojo II	190	52"	4	14°	153 x 15	168/84	Limited Lifetime	Integrated	N/A	N/A	12"	13 1/2"	8"	18
F539	Great Room Traditional	118	72"	5	14°	212 x 25	126/45	Limited Lifetime	Adaptable	3 1/2" & 6"	N/A	80"	12 3/4"	10 1/2"	35
F544	Calais™	127	52"	5	14°	172 x 17	165/62	Limited Lifetime	Integrated	N/A	N/A	8"	12"	7 1/2"	27
F546	Contractor 42"	228	42"	4/5	12°	153 x 10	214/113	Limited Lifetime	Adaptable	4"	N/A	80"	12 1/4"	9 3/4"	14
F547	Contractor 52"	226	52"	4/5	12°	153 x 13	162/67	Limited Lifetime	Adaptable	4"	N/A	80"	12 3/4"	10 1/4"	13
F548	Contractor Uni-Pack	222	52"	4/5	12°	153 x 13	162/56	Limited Lifetime	Included	4"	N/A	80"	17 1/4"	9 3/4"	17
F556	Contractor Plus	216	52"	5	12°	153 x 15	183/69	Limited Lifetime	Adaptable	3 1/2" & 6"	N/A	80"	12 1/4"	10 1/2"	15
F556L	Contractor LED	214	52"	5	12°	153 x 15	183/69	Limited Lifetime	Adaptable	3 1/2" & 6"	N/A	80"	13 1/2"	11 3/4"	15
F562	Supra® 32"	210	32"	6	22°	153 x 16	267/93	Limited Lifetime	Adaptable	3 1/2" & 6"	N/A	80"	12 1/4"	10 1/2"	15
F563	Supra® 44"	208	44"	5	14°	188 x 15	243/77	Limited Lifetime	Adaptable	3 1/2" & 6"	N/A	80"	12 1/4"	10 3/4"	19

Minka-Aire® ceiling fans are warranted to be free from defects in material and workmanship only if purchased from an authorized Minka-Aire® distributor:

Fan motor - Limited Lifetime Warranty to original purchaser with proof of purchase as long as fan remains in its original installation location and is installed using only the original hardware provided (including hanger bracket).

All other parts & controls - warranted to original purchaser with proof of purchase for one (1) year from date of purchase.

		Page Number	Blade Sweep	No. of Blades	Blade Pitch	Motor Size (m/m)	RPM (Hi/Low)	Warranty	Light Kit	Downrods 3/4" I.D.	Downrods 1/2" I.D.	Lead Wire	Dimensions A	Dimensions B	Hanging Weight (lbs)
F563	Supra® 44" -SP	206	44"	5	14°	188 x 15	243/77	Limited Lifetime	Included	3½" & 6"	N/A	80"	12¼"	10¾"	22
F565	Mesa™ 52"	230	52"	5	12°	153 x 14	176/65	Limited Lifetime	Adaptable	N/A	N/A	8"	8¾"	6½"	13
F566	Mesa™ 42"	230	42"	5	12°	153 x 10	211/92	Limited Lifetime	Adaptable	N/A	N/A	8"	7¾"	5¾"	11
F568	Supra® 52"	202	52"	5	14°	188 x 15	179/58	Limited Lifetime	Adaptable	3½" & 6"	N/A	80"	12¾"	10¾"	20
F569	Supra® 52" -SP	200	52"	5	14°	188 x 15	168/53	Limited Lifetime	Included	3½" & 6"	N/A	80"	17"	10¾"	24
F571	Sundance™ 52"	178	52"	5	12°	153 x 15	182/63	Limited Lifetime	Adaptable	3½" & 6"	N/A	80"	12"	11"	16
F572	Sundance™ 42"	179	42"	5	12°	153 x 10	233/103	Limited Lifetime	Adaptable	3½" & 6"	N/A	80"	12¼"	10"	13
F574	Concept™ II Wet 52"	153	52"	3	14°	188 x 20	162/72	Limited Lifetime	Integrated	N/A	N/A	8"	12"	8½"	26
F577	Concept™ I Wet 52"	150	52"	3	14°	188 x 20	160/87	Limited Lifetime	Integrated	3½" & 6"	N/A	80"	15½"	12"	28
F580	Shangri-La®	169	52"	5	14°	188 x 20	172/58	Limited Lifetime	Included	3½" & 6"	N/A	80"	21½"	11½"	35
F581	Gauguin™	170	52"	4	14°	188 x 20	148/76	Limited Lifetime	Integrated	3½" & 6"	N/A	80"	13¾"	13¼"	25
F582	Rainman™	166	54"	5	14°	172 x 20	145/70	Limited Lifetime	Integrated	3½" & 6"	N/A	80"	21¼"	10¾"	28
F588	Ultra-Max™ -SP	198	54"	5	14°	188 x 25	201/65	Limited Lifetime	Adaptable	3½" & 6"	N/A	80"	12¼"	10¾"	24
F589	Sundowner®	174	54"	5	16°	188 x 20	185/51	Limited Lifetime	Adaptable	3½" & 6"	N/A	80"	12½"	10½"	28
F593	Traditional Concept™ 44"	82, 156	44"	3	14°	153 x 17	221/105	Limited Lifetime	Integrated	N/A	N/A	8"	11"	7½"	19
F594	Traditional Concept™ 52"	80, 154	52"	3	14°	172 x 20	178/60	Limited Lifetime	Integrated	N/A	N/A	8"	11"	7½"	23
F596	Cirque™	86	54"	6	14°	188 x 25	143/64	Limited Lifetime	Integrated	4" & 6"	N/A	80"	14¾"	9¾"	26
F598	Airus™	94	54"	5	14°	188 x 18	150/45	Limited Lifetime	Integrated	3½" & 6"	N/A	80"	13½"	8¼"	26
F601	Acero™	88	52"	3	14°	188 x 15	181/62	Limited Lifetime	Integrated	3½" & 6"	N/A	80"	13¼"	9¾"	24
F602	Gyro™	134	42"	6	20°	82 x 25	1350/720	Limited Lifetime	Integrated	3½" & 6"	N/A	80"	13¾"	15¾"	31
F603	Como™	90	54"	5	14°	188 x 20	182/61	Limited Lifetime	Integrated	3½" & 6"	N/A	80"	13¼"	8½"	27
F614	Timeless	104	54"	5	14°	188 x 15	163/58	Limited Lifetime	Adaptable	3½" & 6"	N/A	80"	14"	11¾"	21
F617L	Raptor	6	60"	5	14°	DC172 x 12	150/60	Limited Lifetime	Integrated	3½" & 6"	N/A	80"	11¼"	8½"	29
F620	Bolo™	116	52"	5	14°	172 x 17	168/72	Limited Lifetime	Included	3½" & 6"	N/A	80"	20¼"	12½"	25
F622	Traditional Mojo	186	52"	5	12°	153 x 15	188/79	Limited Lifetime	Included	3½" & 6"	N/A	80"	15"	9¾"	17
F624	Roto XL	146	62"	3	20°	172 x 16	188/96	Limited Lifetime	N/A	4½" & 6"	N/A	80"	10¼"	8¾"	14
F647	Contractor Uni-Pack	218	52"	4/5	12°	153 x 13	160/57	Limited Lifetime	Included	4"	N/A	80"	18"	9¾"	16
F648	Contractor Uni-Pack	220	52"	4/5	12°	153 x 15	188/68	Limited Lifetime	Included	4"	N/A	80"	17¼"	9¾"	17
F656L	Contractor Uni-Pack LED	212	52"	5	12°	172 x 14	197/58	Limited Lifetime	Integrated	3½" & 6"	N/A	80"	14½"	10"	19
F659	Classica	124	54"	5	14°	172 x 16	188/64	Limited Lifetime	Adaptable	3½" & 6"	N/A	80"	14¼"	10½"	23
F672	Iconic™	102	60"	5	12°	188 x 20	148/44	Limited Lifetime	Integrated	3½" & 6"	N/A	80"	14¾"	11¾"	25
F681	Groton	144	56"	5	12°	188 x 25	135/50	Limited Lifetime	Integrated	10"	N/A	80"	20¼"	15½"	38
F688	Kola	110	52"	5	12°	172 x 14	190/61	Limited Lifetime	Adaptable	3½" & 6"	N/A	80"	13"	10¾"	18
F689	Kola-XL	108	60"	5	14°	188 x 20	160/44	Limited Lifetime	Adaptable	3½" & 6"	N/A	80"	13"	10¾"	23
F695	Kafé	114	52"	5	12°	172 x 14	190/61	Limited Lifetime	Adaptable	3½" & 6"	N/A	80"	12½"	10¼"	18
F696	Kafé-XL	112	60"	5	14°	188 x 20	160/44	Limited Lifetime	Adaptable	3½" & 6"	N/A	80"	12½"	10¼"	23
F701	Delano®	98	52"	5	14°	172 x 20	160/65	Limited Lifetime	Integrated	3½" & 6"	N/A	80"	15½"	7½"	28

* Dimensions A & B were measured with the shortest downrod enclosed with the fan (See the Finish Codes fold-out for Picture Diagrams)

Fan Specifications

		Page Number	Blade Sweep	No. of Blades	Blade Pitch	Motor Size (m/m)	RPM (Hi/Low)	Warranty	Light Kit	Downrods 3/4" I.D.	Downrods 1/2" I.D.	Lead Wire	Dimensions A	Dimensions B	Hanging Weight (lbs)
F702	Volterra™	126	52"	5	14°	172 x 20	159/71	Limited Lifetime	Integrated	3½" & 6"	N/A	80"	15¾"	7½"	28
F705	Napoli™	122	56"	5	14°	188 x 25	153/59	Limited Lifetime	Integrated	3½" & 12"	N/A	80"	16½"	8¾"	40
F711	Delano® II	100	52"	5	14°	172 x 20	150/68	Limited Lifetime	Integrated	N/A	N/A	8"	11"	6¼"	25
F715	Napoli™ II	123	68"	5	14°	212 x 25	109/44	Limited Lifetime	Integrated	3½" & 12"	N/A	80"	17"	9¼"	46
F726	Spectre	38	60"	4	14°	DC188 x 10	163/48	Limited Lifetime	Integrated	3½" & 6"	N/A	80"	12¾"	9¼"	18
F727	Rudolph	182	52"	3	14°	172 x 16	139/57	Limited Lifetime	N/A	3½" & 6"	N/A	80"	13"	11"	20
F733	Gilera	68	62"	3	14°	212 x 25	102/39	Limited Lifetime	N/A	3½" & 6"	N/A	80"	13¾"	12½"	29
F734	Strata	164	52"	4	12°	172 x 17	163/81	Limited Lifetime	Integrated	3½" & 6"	N/A	80"	15½"	12"	21
F737	Moda	72	60"	3	20°	DC188 x 14	148/62	Limited Lifetime	N/A	3½" & 6"	N/A	80"	12"	12½"	22
F738	Pancake	14	52"	4	12°	153 x 18	180/70	Limited Lifetime	N/A	6"	N/A	12"	9¾"	7¾"	14
F745	Sabot	46	52"	5	12°	DC172 x 12	173/50	Limited Lifetime	Integrated	3½" & 6"	N/A	80"	9½"	8½"	13
F753	Java	52, 160	54"	3	14°	153 x 18	150/71	Limited Lifetime	N/A	3½" & 6"	N/A	80"	12¼"	10¾"	16
F753L	Java LED	50, 158	54"	3	14°	153 x 18	150/71	Limited Lifetime	Integrated	3½" & 6"	N/A	80"	13¼"	11¾"	17
F759	Classica Gallery Edition	124	54"	5	14°	172 x 16	188/64	Limited Lifetime	Adaptable	3½" & 6"	N/A	80"	18¾"	10¾"	27
F787	Simple	42, 142	52"	3	14°	DC123 x 30	191/148	Limited Lifetime	N/A	3½" & 6"	N/A	80"	10"	8¼"	11
F802	Vintage Gyro™	132	42"	6	20°	82 x 25	1350/720	Limited Lifetime	Integrated	3½" & 6"	N/A	80"	14¼"	15½"	34
F803	Artemis™	8	58"	3	Variable	188 x 25	133/69	Limited Lifetime	Integrated	3½" & 6"	N/A	80"	13"	9½"	26
F812	Lineage™	121	54"	5	14°	188 x 25	193/49	Limited Lifetime	Integrated	3½" & 6"	N/A	80"	18¼"	11¼"	40
F820	Santa Lucia™	120	60"	5	14°	188 x 25	148/72	Limited Lifetime	Integrated	3½" & 6"	N/A	80"	18½"	12¼"	45
F823	Wing	56	52"	1	Variable	DC125 x 30	155/111	Limited Lifetime	N/A	6"	N/A	80"	13"	12¼"	14
F824	Uchiwa	84	56"	3	20°	172 x 25	141/60	Limited Lifetime	Integrated	3½" & 6"	N/A	80"	17¾"	9"	27
F828	Symbio	48	56"	5	15°	DC125 x 30	161/48	Limited Lifetime	Integrated	3½" & 6"	N/A	80"	15¼"	13¼"	16
F833	Kewl	62	52"	3	22°	153 x 15	201/104	Limited Lifetime	N/A	3½" & 6"	N/A	80"	11½"	7½"	12
F838L	Force	4	60"	3	Variable	DC123 x 30	140/60	Limited Lifetime	Integrated	3½" & 6"	N/A	80"	12½"	10"	30
F840	Craftsman™	180	52"	5	14°	172 x 20	170/67	Limited Lifetime	Included	3½" & 6"	N/A	80"	21¼"	13¼"	33
F843	Wave	60	52"	3	48°	172 x 14	153/61	Limited Lifetime	N/A	4½" & 6"	N/A	80"	12½"	8½"	12
F844	Light Wave	58	52"	3	48°	172 x 14	139/57	Limited Lifetime	Integrated	4½" & 6"	N/A	80"	13¾"	8½"	14
F853	Aviation	34	60"	3	Variable	DC120 x 25	115/89	Limited Lifetime	N/A	3½" & 6"	N/A	80"	11½"	9¾"	16
F887	Xtreme 72"	22	72"	9	4°	DC165 x 12	120/51	Limited Lifetime	N/A	3½" & 6"	N/A	80"	11"	9½"	22
F887	Xtreme 80"	22	80"	9	4°	DC165 x 12	100/51	Limited Lifetime	N/A	3½" & 6"	N/A	80"	11"	9½"	23
F887	Xtreme 88"	22	88"	9	4°	DC165 x 12	87/51	Limited Lifetime	N/A	3½" & 6"	N/A	80"	11"	9½"	24
F887	Xtreme 96"	22	96"	9	4°	DC165 x 12	72/51	Limited Lifetime	N/A	3½" & 6"	N/A	80"	11"	9½"	25
F888	Slipstream	30, 140	65"	8	14°	DC165 x 25	98/78	Limited Lifetime	Integrated	3½" & 6"	N/A	80"	14¾"	10½"	25
F889	Slipstream XXL	26, 138	84"	8	14°	DC165 x 25	56/31	Limited Lifetime	Integrated	3½" & 6"	N/A	80"	16"	13"	33
F899L	Ninety-Nine	16	99"	9	Variable	DC172 x 25	59/33	Limited Lifetime	Integrated	3½" & 6"	N/A	80"	13"	9½"	45
F900	Cristafano™	128	68"	5	14°	212 x 25	112/49	Limited Lifetime	Integrated	3½" & 6"	N/A	80"	17¼"	10½"	42
F905	Artemis™ XL5	32	62"	5	28°	DC172 x 25	91/74	Limited Lifetime	Integrated	3½" & 6"	N/A	80"	13¾"	10¼"	21
F1000	Dyno	184	52"	5	12°	153 x 17	175/63	Limited Lifetime	Integrated	3½" & 6"	N/A	80"	12"	9"	15

Minka-Aire® ceiling fans are warranted to be free from defects in material and workmanship only if purchased from an authorized Minka-Aire® distributor:

Fan motor - Limited Lifetime Warranty to original purchaser with proof of purchase as long as fan remains in its original installation location and is installed using only the original hardware provided (including hanger bracket).

All other parts & controls - warranted to original purchaser with proof of purchase for one (1) year from date of purchase.

Minka-Aire® Finishes



AB	Antique Brass
ABD	Brushed Aluminum
BCW	Belcaro Walnut™
BG	Bahama Beige™
BI/AI	Black Iron with Aged Iron Accents
BK	Black
BN	Brushed Nickel
BNW	Brushed Nickel Wet
BS	Brushed Steel
BWH	Bone White
CC	Cognac
CF	Craftsman™
CH	Chrome
CPBR	Copper Bronze
CT	Cattera Bronze™
DBB	Dark Brushed Bronze
DK	Distressed Koa
DKG	Distressed Koa with Gold Highlights
DRB	Dark Restoration Bronze™
DRF	Driftwood
FB	French Beige
GBZ	Golden Bronze
GL	Galvanized
GM	Gun Metal
HT	Heritage™
IBR	Illuminati Bronze™
IO	Iron Oxide
KA	Kocoa
LN	Liquid Nickel
MBK	Matte Black
MCG	Mottled Copper with Gold Highlights
MG	Mahogany Finish
MP	Maple Finish
MW	Mossoro Walnut™
ODK	Distress Koa (Outdoor)
ORB	Oil Rubbed Bronze
ORG	Orange
PBL	Provencal Blanc
PI	Patina Iron
PN	Polished Nickel
PW	Pewter
RD	Red
RRB	Restoration Bronze™
RW	Rosewood
SDBK	Sand Black
SI	Smoked Iron
SL	Silver
STW	Sterling Walnut™
SWH	Shell White
TB	Toned Brass
TL	Translucent
TSP	Tuscan Patina™
VB	Volterra Bronze™
VP	Vineyard Patina
VRT	Vintage Rust™
WA	Weathered Aluminum
WH/44	White
WHF	Flat White

Graphic Design: Minka Group® Graphics
 Product Originals: Minka Group®


Product specifications subject to change at any time.

Minka-Aire®, A Minka Group® Company
Catalog MKACAT2016-03
 Printed in U.S.A.
 © 1993-2016 Minka Lighting, Inc.

Dimensions A and B were measured with the shortest downrod enclosed with the fan.



Minka-Aire® ceiling fans are suitable for year-round use and can contribute to your comfort in the summer and winter. With our reverse switch, in the winter you will be able to move the heat from your ceiling and circulate the air in your living area. In the summer you will save energy by recirculating air from the outside into your room and also if your air conditioning is used, save on energy costs.



We Support



Member





World Headquarters

1151 West Bradford Court, Corona, California 92882

Showroom

Dallas Market Center

2100 Stemmons, Suite 3725, Dallas, TX 75207

951.278.3267 (FANS) 800.307.3267 Fax: 951.278.2828

sales@minkagroup.net | www.minkaaire.com | www.minkagroup.net

\$10.00

