



CHEMICAL & TAPE

- Now with Antibacterial Formula
- Waterless
- Removes Grease, Ink & Paint
- Smooth One Side / Scrubbing Other Side



Tuf Towels are gentle on the hands and are also ideal for cleaning tools at job sites where water is not readily available.



CAT NO	UPC	DESCRIPTION	STD	MSTR	WT/STD	UNIT
TT75	40775	75 Pre-moistened multi-purpose hand towels	6	6	14.75#	Ea

Bag of Rags | PC 6252

- New Bleached White Rags
- Medium Weight
- Soft, Absorbent, Low Lint

Rags are all new material bleached white knit. They are medium weight, random size, soft, absorbent, and are a low linting Premium all purpose wiper.



CAT NO	UPC	DESCRIPTION	STD	MSTR	WT/STD	UNIT
RGZ2	11922	2 Pound bag white knit rags	1	10	2.10#	Ea

Premium Color Coding PVC Tape | PC 5330

- UL Listed
- 7.5 Mil 3/4" x 66 Ft.
- 600 Volt Rated - 80° C, 176° F
- Individual Cello Wrap - 10 Per STD Sleeve
- Weather & Cold Resistant
- Flame Retardant

PVC Tape is used for insulation and protection over wires and connectors or over splicing and filler compounds; the holding of high voltage electrical appliances; color code identification; wire harnessing and home maintenance.



CAT NO	UPC	DIMENSIONS	COLOR	STD	MSTR	WT/STD	UNIT
66CBLU	59650	3/4" x 66'	Blue	10	100	2.22#	Ea
66CBRN	59651	3/4" x 66'	Brown	10	100	2.22#	Ea
66CGRN	59652	3/4" x 66'	Green	10	100	2.22#	Ea
66CGRY	59653	3/4" x 66'	Gray	10	100	2.22#	Ea
66CORG	59654	3/4" x 66'	Orange	10	100	2.22#	Ea
66CRED	59655	3/4" x 66'	Red	10	100	2.22#	Ea
66CWHT	59656	3/4" x 66'	White	10	100	2.22#	Ea
66CYEL	59657	3/4" x 66'	Yellow	10	100	2.22#	Ea
Premium Black PVC Tape							
99 PC	15431	3/4" x 66'	Black	10	100	2.22#	Ea

Economy PVC Tape | PC 5350

- UL Listed
- 7 Mil 3/4" x 60 Ft.
- 600 Volt Rated, 80° C - 176° F
- Individual Cello Wrap - 10 Per STD Sleeve

PVC Tape is used for insulation and protection over wires and connectors or over splicing and filler compounds; the holding of high voltage electrical appliances; wire harnessing and home maintenance.



CAT NO	UPC	DIMENSIONS	COLOR	STD	MSTR	WT/STD	UNIT
360	15890	3/4" x 60'	Black	10	200	1.81#	Ea

See new products at www.lhdottie.com

UPC Vendor ID Code: 78-1002



Duct Tape | PC 5380



Duct Tape will adhere to all types of surfaces. The polyethylene coated cloth construction provides superior mechanical strength and conforms well to irregular surfaces. It is excellent for bundling, patching and sealing. It tears straight and is curl resistant.

- 2" x 60 Yards
- Temperature Rating 200° F
- 9 Mil - Cloth Backing
- Individual Cello Wrap

CAT NO	UPC	DIMENSIONS	COLOR	STD	MSTR	WT/STD	UNIT
DT260	28100	2" x 60 yds	Silver	12	24	19.50#	Ea

Rubber Tape | PC 5370



Rubber Tape is used in combination with friction and vinyl tape for primary insulation up to 600 volts and for use around split bolt connections, terminal lugs and compression connectors. It is used in insulating and waterproof applications, and easily conforms to irregular shapes and surfaces yielding a void free, electrically stable buildup. It is compatible with all extruded dielectric cable insulations.

- UL Listed
- 30 Mil
- 3/4" x 22 Ft.
- 600 Volt Rated

CAT NO	UPC	DIMENSIONS	STD	MSTR	WT/STD	UNIT
822	28120	3/4" x 22'	10	100	3.60#	Ea

Friction Tape | PC 5360



Friction Tape is used for providing mechanical protection against abrasion and penetration of cable, splices and wire. Also used as a temporary binding and harnessing tape and a multitude of miscellaneous general purpose uses. When applied over tool handles, it effects a non-slip surface.

- UL Listed
- 3/4" x 60 Ft.
- 600 Volt Rated
- Adhesive Compound on Both Sides

CAT NO	UPC	DIMENSIONS	STD	MSTR	WT/STD	UNIT
860	28130	3/4" x 60'	10	100	3.20#	Ea

Pipe Wrap (PVC) | PC 5420



Pipe Wrap is a polyvinyl chloride film coated with a rubber resin adhesive which protects pipe, joints, conduit and couplings for overhead or direct burial applications. It is corrosion and puncture resistant.



Plumbing Code

- 1", 2" & 4" Widths
- UPC Approved
- 10 Mil and 20 Mil
- Abrasion Resistant
- Provides Electrical Protection

CAT NO	UPC	DIMENSIONS	MIL	STD	MSTR	WT/STD	UNIT
110	28110	1" x 100'	10 Mil	48	48	29.28#	Ea
210	28140	2" x 100'	10 Mil	24	24	28.80#	Ea
410P	28142	4" x 100'	10 Mil	12	12	27.60#	Ea
220	28145	2" x 100'	20 Mil	24	24	53.52#	Ea

Masking Tape | PC 5410



Masking Tape is a general purpose tape which is tan in color and is supplied for indoor applications. The outdoor version is blue in color and UV resistant. It has a low tack and is easily removed where application and cleanup are several days apart.

- 3/4", 1", 1-1/2" & 2"
- 60 Yard Rolls

CAT NO	UPC	DIMENSIONS	STD	MSTR	WT/STD	UNIT	
Masking Tape							
75-MT	30005	3/4" x 60 yds	48	48	11.52#	Ea	
100-MT	30010	1" x 60 yds	36	36	10.80#	Ea	
150-MT	30015	1-1/2" x 60 yds	24	24	12.00#	Ea	
200-MT	30020	2" x 60 yds	24	24	15.12#	Ea	

Outdoor Masking Tape (Blue)

200-MT Blue	28143	2" x 60 yds	24	24	16.68#	Ea
-------------	-------	-------------	----	----	--------	----

Outdoor or Direct Sunlight. Easy Clean Up, Low Tack, UV Resistant



- Non Adhesive Polyethylene
- Continuous Warning
- 4 Mil
- 3" or 6" Widths x 1,000 Ft.
- Custom Legends Available

Underground Tape protects buried utility lines and is placed 12" above buried pipes, cables and conduits before final backfilling. Other legends, colors on request.



CAT NO	UPC	LEGEND	COLOR	STD	MSTR	WT/STD	UNIT
3" x 1,000 Feet 4 Mil							
UT4D	16704	Caution Buried Cable TV Line Below	Orange	1	12	4.49#	Ea
UT7D	16340	Caution Buried Electric Line Below	Yellow	1	12	4.49#	Ea
UT8D	16342	Caution Buried Electric Line Below	Red	1	12	4.49#	Ea
UT11D	16711	Caution Buried High Voltage Line Below	Yellow	1	12	4.49#	Ea
UT12D	16712	Caution Buried High Voltage Line Below	Red	1	12	4.49#	Ea
UT17D	16717	Caution Buried Telephone Line Below	Orange	1	12	4.49#	Ea
UT19D	16719	Caution Buried Utilities Underground	Yellow	1	12	4.49#	Ea
UT20D	16720	Caution Buried Utility Line Below	Yellow	1	12	4.49#	Ea
UT43D	16743	Caution Buried Cable Line Below	Orange	1	12	4.49#	Ea
UT44D	16744	Caution Buried Fiber Optic Line Below	Orange	1	12	4.49#	Ea
6" x 1,000 Feet 4 Mil							
UT25D	16725	Caution Buried Cable TV Line Below	Orange	1	6	9.02#	Ea
UT28D	16344	Caution Buried Electric Line Below	Yellow	1	6	9.02#	Ea
UT29D	16346	Caution Buried Electric Line Below	Red	1	6	9.02#	Ea
UT32D	16732	Caution Buried High Voltage Line Below	Yellow	1	6	9.02#	Ea
UT33D	16733	Caution Buried High Voltage Line Below	Red	1	6	9.02#	Ea
UT38D	16738	Caution Buried Telephone Line Below	Orange	1	6	9.02#	Ea
UT40D	16740	Caution Buried Utilities Underground	Yellow	1	6	9.02#	Ea
UT41D	16741	Caution Buried Utility Line Below	Yellow	1	6	9.02#	Ea
UT46D	16746	Caution Buried Cable Line Below	Orange	1	6	9.02#	Ea
UT47D	16747	Caution Buried Fiber Optic Line Below	Orange	1	6	9.02#	Ea

HAZARD TAPE

- Reusable Polyethylene
- Continuous Warning
- 3 Mil
- 3" Wide x 1,000 or 300 Ft.
- Custom Legends Available

Barricade Tape is used for marking physical hazards or off limit areas. Other legends, colors on request. Meets OSHA 1910.144 for marking physical hazards.



CAT NO	UPC	LEGEND	COLOR	STD	MSTR	WT/STD	UNIT
3" x 1,000 Feet							
BT5	16330	Caution Caution Caution	Yellow	1	12	4.86#	Ea
BT8	16332	Caution Do Not Enter	Yellow	1	12	4.86#	Ea
BT12	16335	Caution High Voltage	Yellow	1	12	4.86#	Ea
BT13	16334	Caution Keep Out	Yellow	1	12	4.86#	Ea
BT19	16336	Caution Open Trench	Yellow	1	12	4.86#	Ea
BT31	16338	(Alternating Stripes)	Black/Yellow	1	12	4.86#	Ea
BT32	16339	(Alternating Stripes)	Red/White	1	12	4.86#	Ea
BT49	16387	Danger Keep Out	Red	1	12	4.86#	Ea
3" x 300 Feet							
BT5X3	16331	Caution Caution Caution	Yellow	1	12	1.36#	Ea
BT8X3	16333	Caution Do Not Enter	Yellow	1	12	1.36#	Ea
BT13X3	16337	Caution Keep Out	Yellow	1	12	1.36#	Ea

Detectable Tape see: D4






Detectable Tape protects buried utility lines and is placed above buried pipes, cables and conduits. It is easily located with any common metal detector, for use before you dig; its highly visible colors make it easy to locate after the dig has begun. Other legends, colors on request.

- Foil Bonded Polyethylene
- Continuous Warning
- 5 Mil
- 3" and 6" Widths x 1,000 Ft.
- Custom Legends Available

CAT NO	UPC	LEGEND	COLOR	STD	MSTR	WT/STD	UNIT
3" x 1,000 Feet							
DU01	16350	Caution Buried Electric Line Below	Red	1	12	6.07#	Ea
DU05	16360	Caution Buried Telephone Line Below	Orange	1	12	6.07#	Ea
DU08	16364	Caution Buried CATV Line Below	Orange	1	12	6.07#	Ea
DU09	16366	Caution Buried High Voltage Line Below	Red	1	12	6.07#	Ea
DU10	16368	Caution Buried Fiber Optic Line Below	Orange	1	12	6.07#	Ea
6" x 1,000 Feet							
DU601	16352	Caution Buried Electric Line Below	Red	1	6	13.72#	Ea
DU605	16370	Caution Buried Telephone Line Below	Orange	1	6	13.72#	Ea
DU608	16372	Caution Buried CATV Line Below	Orange	1	6	13.72#	Ea
DU609	16374	Caution Buried High Voltage Line Below	Red	1	6	13.72#	Ea
DU610	16376	Caution Buried Fiber Optic Line Below	Orange	1	6	13.72#	Ea

Velcro™ Hook & Loop Ties | PC 5975



Velcro™ Hook & Loop ties are ideal for wire and cable assemblies, fiber optics, networks and electronic/electrical products.

- Green
- Soft to the Touch
- Reusable
- Infinitely Adjustable
- 8" Perforated Rolls or 15 Ft. Linear Rolls

CAT NO	UPC	WIDTH / LENGTH	COLOR	STD	MSTR	WT/STD	UNIT
Linear Rolls / Can Be Cut To Desired Length							
DT15V	23196	1/2" x 15'	Green	1	10	.068#	Ea
Linear Rolls / Contains 25 Pre-Cut 8" Velcro™ Ties							
DT8V	23195	1/2" x 16'	Green	1	10	.050#	Ea

Warehouse Supplies | PC 5400

CAT NO	UPC	WIDTH / LENGTH / DESCRIPTION	STD	MSTR	WT/STD	UNIT
Stretch Film						
SF18	24030	18" x 1500' 80 Gauge Stretch Film For Wrapping Palletized Products	4	4	38.68#	Ea
Carton Sealing Tape						
2110CL	59802	2" x 110 yds Clear Polypro Use in dispenser to easily seal cartons	36	36	16.20#	Ea
Tape Dispenser						
TD	59800	Dispenser Only Handles 2" wide Carton Sealing Tape	1	1	1.10#	Ea



- Nylon™ 6/6
- Natural White
- UV Rated Black
- Fasten wires, hoses, ducts and cables

Patented double locking design adds 50% more tensile strength than the industry standard. Black cable ties are UV Rated to resist degradation by Ultraviolet rays. Nylon™ 6/6 remains serviceable in temperature ranges of -40° to 185°F. Meets Flammability Classification UL-94 V-2. Recognized under component program of Underwriters Laboratories.



CAT NO	UPC	COLOR	TENSILE	BUNDLE RANGE	LENGTH	WIDTH	STD	MSTR	WT/STD	UNIT
--------	-----	-------	---------	--------------	--------	-------	-----	------	--------	------

Standard Duty / Bent Tip

DT4	50004	Natural	18 lbs	13/16"	4"	3/32"	100	1000	.07#	C
DT5	50005	Natural	45 lbs	1-3/8"	6"	1/8"	100	1000	.14#	C
DT6	50006	Natural	75 lbs	2"	8"	5/32"	100	1000	.29#	C
DT11	50011	Natural	75 lbs	3"	11"	5/32"	100	1000	.38#	C
DT14	50014	Natural	75 lbs	4"	14"	5/32"	100	1000	.48#	C

DT4B	50504	UV Black	18 lbs	13/16"	4"	3/32"	100	1000	.07#	C
DT5B	50505	UV Black	45 lbs	1-3/8"	6"	1/8"	100	1000	.14#	C
DT6B	50506	UV Black	75 lbs	2"	8"	5/32"	100	1000	.29#	C
DT11B	50511	UV Black	75 lbs	3"	11"	5/32"	100	1000	.38#	C
DT14B	50514	UV Black	75 lbs	4"	14"	5/32"	100	1000	.48#	C

Heavy Duty / Straight Tip

DT14H	51014	Natural	120 lbs	4"	15"	9/32"	50	500	.52#	C
DT21H	51021	Natural	175 lbs	6"	21-1/2"	9/32"	50	500	.87#	C
DT34H	51034	Natural	175 lbs	11"	36"	9/32"	50	500	1.54#	C

DT14HB	51514	UV Black	120 lbs	4"	15"	9/32"	50	500	.52#	C
DT21HB	51521	UV Black	175 lbs	6"	21-1/2"	9/32"	50	500	.87#	C
DT34HB	51534	UV Black	175 lbs	11"	36"	9/32"	50	500	1.54#	C

CAT NO	UPC	COLOR	TENSILE	RANGE	MTG. HOLE	LENGTH	WIDTH	STD	MSTR	WT/STD	UNIT
--------	-----	-------	---------	-------	-----------	--------	-------	-----	------	--------	------

Standard Mounting / Bent Tip

DTM6	52006	Natural	50 lbs	1-3/4"	#10	7"	5/32"	100	1000	.34#	C
DTM14	52014	Natural	50 lbs	4"	1/4"	14"	5/32"	100	1000	.52#	C
DTM6B	52506	UV Black	50 lbs	1-3/4"	#10	7"	5/32"	100	1000	.35#	C
DTM14B	52514	UV Black	50 lbs	4"	1/4"	14"	5/32"	100	1000	.52#	C

Adhesive Mounting Bases | PC 5970

- Nylon™ 6/6
- Natural White
- UV Rated Black

Adhesive backed mounting bases are used for securing wire and cable bundles. Center screw hole provides extra holding power. Molded from durable Nylon™ 6/6 material. Four sided design allows ties to be easily inserted from any angle.



CAT NO	UPC	COLOR	SIZE	STD	MSTR	WT/STD	UNIT
--------	-----	-------	------	-----	------	--------	------

DT75S	51075	Natural	3/4" x 3/4"	100	1000	.20#	C
DT100S	51100	Natural	1" x 1"	100	1000	.50#	C
DT75SB	51076	UV Black	3/4" x 3/4"	100	1000	.20#	C
DT100SB	51102	UV Black	1" x 1"	100	1000	.50#	C

Dot-Pak | PC 5970

- Natural White
- UV Rated Black
- Assorted Ties
- Zip Lock Pouch

Dot-Pak is an assortment of 500 ties in a Zip Lock Pouch and includes 6", 8" and 11" sizes.



CAT NO	UPC	CONTENTS	COLOR	STD	MSTR	WT/STD	UNIT
--------	-----	----------	-------	-----	------	--------	------

450	15970	200 DT-5 • 200 DT-6 • 100 DT-11	Natural	1	6	1.00#	Ea
450B	15972	200 DT-5B • 200 DT-6B • 100 DT-11B	UV Black	1	6	1.00#	Ea

See new products at www.lhdottie.com

UPC Vendor ID Code: 78-1002





Polypropylene Pull Rope is a light-weight, strong rope that is rot proof and unaffected by water, oil, gasoline and most chemicals.

- Polypropylene
- Safety Yellow

CAT NO	UPC	SIZE	WORK LOAD	TENSILE	STD	MSTR	WT/STD	UNIT
18-100	61300	1/8" x 1000'	48#	480#	1	1	4.05#	Ea
18-250	61305	1/8" x 2500'	48#	480#	1	1	10.58#	Ea
36-25	61302	3/16" x 250'	72#	720#	1	1	2.69#	Ea
36-60	61304	3/16" x 600'	72#	720#	1	1	6.52#	Ea
36-100	61306	3/16" x 1000'	72#	720#	1	1	9.39#	Ea
36-120	61308	3/16" x 1200'	72#	720#	1	1	10.62#	Ea
36-300	60314	3/16" x 3000'	72#	720#	1	1	23.47#	Ea
36-360	60316	3/16" x 3600'	72#	720#	1	1	30.78#	Ea
14-25	61310	1/4" x 250'	113#	1130#	1	1	4.99#	Ea
14-60	61312	1/4" x 600'	113#	1130#	1	1	8.96#	Ea
14-100	61314	1/4" x 1000'	113#	1130#	1	1	15.72#	Ea
14-120	61316	1/4" x 1200'	113#	1130#	1	1	17.84#	Ea
14-240	61313	1/4" x 2400'	113#	1130#	1	1	34.02#	Ea
14-400	61315	1/4" x 4000'	113#	1130#	1	1	51.54#	Ea
38-30	61318	3/8" x 300'	243#	2430#	1	1	8.93#	Ea
38-60	61320	3/8" x 600'	243#	2430#	1	1	18.55#	Ea
38-120	61322	3/8" x 1200'	243#	2430#	1	1	36.92#	Ea
38-250	60312	3/8" x 2500'	243#	2430#	1	1	70.00#	Ea
38-360	60318	3/8" x 3600'	243#	2430#	1	1	111.00#	Ea
12-30	61324	1/2" x 300'	378#	3780#	1	1	16.98#	Ea
12-60	61326	1/2" x 600'	378#	3780#	1	1	33.10#	Ea
12-120	61328	1/2" x 1200'	378#	3780#	1	1	62.22#	Ea

PULLING PRODUCTS



Pull Line is used to pull rope through conduit and can be used with power fishing systems.

- Two Ply Pull Line
- Dispensing Box
- Dispensing Pail
- Rot & Mildew Resistant

CAT NO	UPC	COLOR	LENGTH	WORK LOAD	TENSILE	STD	MSTR	WT/STD	UNIT
6502	15745	Blue / White	6500'	20#	200#	1	1	10.00#	Ea
6502P	15747	Blue / White	6500' Pail	20#	200#	1	1	11.65#	Ea
Heavy Duty									
2203P	27506	Red / White	2200' Pail	50#	500#	1	1	12.66#	Ea



Polypropylene Pull Rope is lightweight and strong. Polypropylene floats, and is the most resistant of any other rope. For most requirements, polypropylene is the most economical rope to use.

Polyester Pull Line/Measuring Tape provides a lower coefficient of friction than other competitive tapes due to special prelubrication and high abrasion yarns. It is provided with accurate sequential footage markings. It is soft to the touch and comfortable to handle.

Nylon Fish Line resists rot and mildew.



- Polyester
- Sequentially Marked
- Pre-Lubed
- Abrasion Resistant

Polyester pull line/measuring tape is a very strong synthetic with excellent abrasion resistance. Polyester does not have the stretch and elasticity of nylon, but is superior to nylon with respect to cycle loading and abrasion. Pre-lubed and low friction, it provides a softer feel for easier handling by linemen.



CAT NO	UPC	SIZE	TENSILE	STD	MSTR	WT/STD	UNIT
DWP500	27557	1/2" x 500'	1250#	1	4	6.28#	Ea
DWP1500	27558	1/2" x 1500'	1250#	1	1	16.78#	Ea
DWP3000	27559	1/2" x 3000'	1250#	1	1	28.25#	Ea
DWP501	27500	5/8" x 500'	1800#	1	4	8.78#	Ea
DWP1501	27501	5/8" x 1500'	1800#	1	1	22.20#	Ea
DWP3001	27502	5/8" x 3000'	1800#	1	1	36.45#	Ea
DWP502	27503	3/4" x 500'	2500#	1	4	13.50#	Ea
DWP1502	27504	3/4" x 1500'	2500#	1	1	27.50#	Ea
DWP3002	27505	3/4" x 3000'	2500#	1	1	48.42#	Ea
PGE3000	61331	1/4" x 3000'	400#	1	1	14.00#	Ea

Conduit Measuring Tape | PC 6031

- Polyester
- Sequentially Marked
- Abrasion Resistant

Conduit measuring tape allows you to fish and measure conduit runs in one operation. It is sequentially marked in one foot increments and made of strong waterproof polyester. It may be fished into conduit and allowed to remain over an extended period of time for further use.



CAT NO	UPC	LENGTH	WORK LOAD	TENSILE	STD	MSTR	WT/STD	UNIT
3000	30000	3000'	14#	140#	1	4	4.18#	Ea

Nylon Fishing Line | PC 6060

- Center Feed
- Fits Most Canister Systems
- Mildew Resistant
- 2150 Ft. Length
- 85 lb Tensile Strength

Nylon fishing line with a center feed and fast pay-out can be pulled into the run and left to add future wires. Excellent resistance to rot, abrasion, mildew, marine growth, petroleum products and most chemicals.



CAT NO	UPC	LENGTH	TENSILE	STD	MSTR	WT/STD	UNIT
N85	17880	2150'	85#	1	12	1.23#	Ea

Heavy Duty Nylon Fishing Line | PC 6060

- 100% Filament / #36 Nylon
- Rot Resistant
- 580 Ft Length
- 310 lb Tensile Strength

Heavy Nylon fish line is used where a higher tensile strength is required. It can be pulled into the run and left to add future wires.



CAT NO	UPC	LENGTH	TENSILE	STD	MSTR	WT/STD	UNIT
N36	17881	580'	310#	1	6	1.04#	Ea

See new products at www.lhdottie.com

UPC Vendor ID Code: 78-1002



PULLING PRODUCTS



Line packages combine piston and string in a single package. With a portable blower you can blow or vacuum the nylon line and pull a rope through.

- Nylon Line
- Color Coded
- 17 lb Tensile Strength

CAT NO	UPC	DIAMETER / LENGTH	COLOR	STD	MSTR	WT/STD	UNIT
LP5075	32220	1/2" x 75'	Red	10	100	.09#	Ea
LP50150	32202	1/2" x 150'	Red	10	100	.12#	Ea
LP7575	32204	3/4" x 75'	Yellow	10	100	.09#	Ea
LP75200	32206	3/4" x 200'	Yellow	5	50	.08#	Ea
LP75300	32208	3/4" x 300'	Yellow	5	50	.13#	Ea
LP75450	32210	3/4" x 450'	Yellow	5	50	.18#	Ea
LP10075	32212	1" x 75'	White	10	50	.09#	Ea
LP100200	32214	1" x 200'	White	5	50	.10#	Ea
LP100300	32216	1" x 300'	White	5	25	.14#	Ea
LP100450	32218	1" x 450'	White	5	25	.17#	Ea

Power Fishing Pistons | PC 6040

REUSABLE



Power fishing pistons are used with a vacuum power or blower to pull line through a conduit run. It fits most conduits 1/2" through 6". The 1/2", 3/4" & 1" sizes have metal pulling eyes at both ends. Other sizes have a hook on one end and an eye on the opposite end. Tough foam piston cleans its own path and provides an air-tight seal.

- Durable Foam
- Steel Eye

CAT NO	UPC	DESCRIPTION	STD	MSTR	WT/STD	UNIT
PFP50	32030	1/2" Conduit	5	25	.19#	Ea
PFP75	32032	3/4" Conduit	5	25	.20#	Ea
PFP100	32034	1" Conduit	5	10	.21#	Ea
PFP125	32036	1-1/4" Conduit	2	10	.32#	Ea
PFP150	32038	1-1/2" Conduit	1	5	.27#	Ea
PFP200	32040	2" Conduit	1	5	.43#	Ea
PFP250	32042	2-1/2" Conduit	5	5	.43#	Ea
PFP300	32044	3" Conduit	5	5	.57#	Ea
PFP350	32046	3-1/2" Conduit	2	2	.50#	Ea
PFP400	32048	4" Conduit	2	2	.55#	Ea
PFP500	32050	5" Conduit	2	2	.63#	Ea
PFP600	32052	6" Conduit	2	2	.68#	Ea

Display Pack

TECH TALK


Dottie Quick Sticks

Quick Sticks screw together to reach full or desired length. Use to fish wires through walls, under floors, over suspended ceilings and into many other confined spaces. Quick Sticks will flex up to 90° without breaking. Made from high strength, low weight fiber glass material. Quick Sticks are ideal for pulling and stringing communication wires, alarm system wires, romex, telephone and thermostat wire. Available attachments are; Pulling Hooks, Pulling Eyes and Whisk Heads. Our glow in the dark version is available in 3/16" & 1/4" diameter. See page E31.



- Polymers and Butyl Rubber
- Gray
- 100% Solid
- Low Odor
- Temperature Range: -20° F. to 180° F.

- Sound Barrier
- Non Hardening
- Flexible
- Forms Watertight Seal



CAT NO	UPC	SIZE	STD	MSTR	WT/STD	UNIT
68	15250	1/8 x 6 x 8"	100	100	33.80#	C



Insulpads are used on electrical outlet boxes, under moldings, around windows, doors and vents; or wherever metal overlaps metal. It is used to seal nail and knockout holes in boxes and to prevent air transmitted sound. It is heavy mastic which is flexible, and can be pressed into any shape to form a water and airtight seal. It is non hardening and remains pliable as applied or packaged. Insulpads are supplied on a special silicone treated release paper.

Duct Seal | PC 6130

- UL Listed
- Adheres to Most Clean Surfaces
- Non Toxic / Asbestos Free

Duct Seal (Prest "O" Seal) is used to seal around junction box flashings, service masts, etc. It is heavy mastic, which is flexible and can be pressed into any shape to form a water and airtight seal.



CAT NO	UPC	SIZE	STD	MSTR	WT/STD	UNIT
LHD1	17230	1 lb	50	50	50.00#	Ea
LHD5	17235	5 lb	10	10	50.00#	Ea

ABS & PVC Cement | PC 6170

- Virgin PVC Resin
- Clear or Gray
- Reduced Emission VOC
- Pint or Quart

Low VOC (Volatile Organic Compound) ABS & PVC Cement conform to South Coast Air Quality Management District regulations (Rule 1168), and are used for electrical conduits and non pressure applications. All conduit schedules & classes through 6". Joins ABS to PVC, ABS to ABS, PVC to PVC.



CAT NO	UPC	CONTENTS	COLOR	STD	MSTR	WT/STD	UNIT
PV16CL	30950	Pint	Clear	12	12	14.64#	Ea
PV16GR	30955	Pint	Gray	12	12	14.64#	Ea
PV32CL	30960	Quart	Clear	12	12	26.88#	Ea
PV32GR	30965	Quart	Gray	12	12	26.88#	Ea

ABS & PVC Primer | PC 6170

- Thin Solvent
- Purple
- Fast Acting
- Pint

ABS & PVC Primer is a water thin solvent to be used in conjunction with PVC cement to produce the best PVC joint possible. It also acts as a cleaner as well as a pre-softener, and is suitable for use on all types, classes, and schedules of PVC pipes and fittings.



CAT NO	UPC	CONTENTS	COLOR	STD	MSTR	WT/STD	UNIT
PR16	30975	Pint	Purple	12	12	13.56#	Ea

See new products at www.lhdottie.com

UPC Vendor ID Code: 78-1002





- UL Classified
- Asbestos Free
- Red
- 1 to 4 Hour Rating
- Remains Flexible
- Non Sagging
- Non Toxic-No VOC's
- Interior Use

CAT NO	UPC	CONTENTS	COLOR	STD	MSTR	WT/STD	UNIT
MC150	16356	10.3 oz.	Red	24	24	30.24#	Ea
1000D	16386	10.3 oz.	Red	24	24	25.20#	Ea

TECH TALK

Fire Stop Caulking Compounds are water based, flexible, highly intumescent, fire rated sealants. They prevent the spread of fire and smoke through joints in fire rated gypsum wall board partitions, concrete block or concrete walls and/or concrete or corrugated steel deck floor/ceiling assemblies. #MC150+ is a general dry caulk rated to a maximum 3 hour fire rating. The #1000D is a premium caulk rated to a maximum 4 hour fire rating.

Fire Rated Putty Pads | PC 6140



- UL Listed
- Asbestos Free
- Red
- 1 to 2 Hour Rating
- Water Resistant
- Intumescent Activated at 220° F.
- Sound Barrier
- Adheres to all Common Building Surfaces
- 1 to 2 Hour Rating

CAT NO	UPC	SIZE	STD	MSTR	WT/STD	UNIT
FRP67	16378	6 x 7 x 1/8"	20	20	7.20#	Ea

TECH TALK

Fire Rated Putty is used on electrical outlet boxes and cabinets to maintain the hourly rating of fire rated walls and to prevent passage of smoke, flame and toxic gases. The pads are intumescent (swells when heated forming an insulating char) and can be pressed into any shape to form a water and airtight seal. Only one 1/8" pad is required for a one to two hour fire rating

Firesticks | PC 6140



- UL Listed
- Asbestos Free
- Red
- 1 to 2 Hour Rating
- Water Resistant
- Intumescent Activated at 220° F.
- Sound Barrier
- Adheres to all Common Building Surfaces
- 1 to 2 Hour Rating

CAT NO	UPC	SIZE	STD	MSTR	WT/STD	UNIT
FRS18	16380	18 cu. in.	12	12	0.77#	Ea

TECH TALK

Firesticks are used to seal around items that penetrate through fire rated walls and floors, including construction joints and blank openings. It is used with electrical cables, conduit and metal pipe. Firesticks are hand moldable with no curing time required, and will not dry out. They can be reused as additional penetrating items are removed or installed.

Fire Stop Pillows | PC 6160



Fire Stop Pillows are intumescent (swells when heated) and designed for use primarily in large openings with wire cables, cable trays, blank openings or multiple penetrating items.

- UL Classified
- Intumescent
- 1 to 2 Hour Rating

CAT NO	UPC	SIZE	STD	MSTR	WT/STD	UNIT
1030P	16384	2 x 9 x 6"	1	10	0.59#	Ea
1040P	16385	3 x 9 x 6"	1	10	1.05#	Ea

To Order: Phone (323) 725-1000 / Fax (323) 721-0000



Handi-Foam Expanding Sealant | PC 6190

- UL Classified
- ICBO Approved
- Polyurethane
- Pressurized Can
- Quick Drying

Handi-Foam is an expanding sealant which is a moisture-cure polyurethane foam. It is used to seal, bond, retrofit, insulate and deaden sound in electrical, plumbing, air-conditioning and refrigeration applications. It expands 2 to 3 times its extruded bead, and is rated R-5 for each inch of foam. Specifically designed to be dispensed as a bead for filling cracks. Substrate must be clean, firm, free of loose particles and dust.



CAT NO	UPC	CONTENTS	STD	MSTR	WT/STD	UNIT
HF340	90980	12 oz.	12	12	12.12#	Ea

RTV Silicone Sealant | PC 6200

- UL Classified
- Clear / White
- Neutral Cure Silicone
- Non Acetic & Non Corrosive
- Low Odor

- Flexible, Non Sagging, Watertight
- Withstands temperatures to 450° F



CAT NO	UPC	COLOR	CONTENTS	DESCRIPTION	STD	MSTR	WT/STD	UNIT
RTV3	17360	Clear	3 oz.	Tube	12	12	3.60#	Ea
RTV8	17366	Clear	7.25 oz.	Pressurized Can	12	12	4.53#	Ea
RTV10	17365	Clear	10.1 oz.	Cartridges	12	12	9.48#	Ea
RTV8W	10921	White	7.25 oz.	Pressurized Can	12	12	4.53#	Ea
RTV10W	17367	White	10.1 oz.	Cartridges	12	12	9.48#	Ea



100% RTV Silicone Sealant contains no solvents or fillers. It is provided in a pressurized can, 3 oz. tube or as a 10 oz. caulk. It is perfect for exterior and interior sealing and caulking, and adheres to metal, glass, marble, tile, ceramic, porcelain, painted surfaces, non oily woods, plastic and rubber. RTV is mildew resistant and can be used as an adhesive for bonding surfaces together.

Roof Mastic | PC 6210

- UL Classified
- Asbestos Free
- Meets ASTM 4586, ASTM D2822
- Meets Federal Specs SS-C-153

Premium grade roof mastic can be used in wet or dry locations to patch cracks & breaks, repair seams & joints and for sealing flashings. It adheres to all surfaces, wet or dry and forms a tight, strong weathertight seal which stays soft and pliable. Applied with a trowel or putty knife, it will cure to be a durable, resilient coating of excellent adhesion and unsurpassed weathering.



CAT NO	UPC	CONTENTS	STD	MSTR	WT/STD	UNIT
RKM1	30605	1 Quart	12	12	30.60#	Ea
RKM4	30610	1 Gallon	4	4	38.52#	Ea
RKM20	30615	5 Gallon	1	1	43.94#	Ea
RKM10	10920	10 oz.	12	12	9.48#	Ea

Dark Cutting Oil | PC 6220

- Petroleum Mineral Oil
- Chlorinated Additive

Dark Cutting Oil is specifically designed for threading steel and cast iron, and is recommended for cutting ferrous materials and ferrous alloys. It has been fortified with a chlorinated additive which works as an extreme pressure agent to allow an increased tolerance of alloyed or hard-grained pipe. Caution: Dark cutting oil contains active sulphur which will stain non-ferrous materials including copper, brass, stainless.



CAT NO	UPC	CONTENTS	STD	MSTR	WT/STD	UNIT
CO1	27525	1 Quart	12	12	24.96#	Ea
CO4	27530	1 Gallon	4	4	32.04#	Ea

See new products at www.lhdottie.com

UPC Vendor ID Code: 78-1002





Voltage markers are used to prevent dangerous mistakes as well as identify conduit, cable trays, load centers, busways, circuit breakers, fuse boxes, switches and other vital equipment. They eliminate costly trial and error searches.


- Prevent Dangerous Mistakes
- Identify Conduit, Cable Trays, Load Centers, Busways, Circuit Breakers, Switches, Fuse Boxes and Other Vital Electrical Equipment
- Eliminate Trial and Error Searches
- Protects Costly Equipment

Style A: 1 Per Card		Style B: 4 Per Card		Style C: 18 Per Card		5 Cards Per Standard Package Priced Per Package	
CAT NO	UPC	CAT NO	UPC	CAT NO	UPC	LEGEND	UNIT
VM110A	41000	VM110B	41029	VM110C	41058	110 Volts	Ea Pack
VM115A	41001	VM115B	41030	VM115C	41060	115 Volts	Ea Pack
VM120A	41002	VM120B	41031	VM120C	41061	120 Volts	Ea Pack
VM208A	41003	VM208B	41032	VM208C	41062	208 Volts	Ea Pack
VM220A	41004	VM220B	41033	VM220C	41063	220 Volts	Ea Pack
VM230A	41005	VM230B	41034	VM230C	41064	230 Volts	Ea Pack
VM240A	41006	VM240B	41035	VM240C	41065	240 Volts	Ea Pack
VM250A	41007	VM250B	41036	VM250C	41066	250 Volts	Ea Pack
VM277A	41008	VM277B	41037	VM277C	41067	277 Volts	Ea Pack
VM440A	41009	VM440B	41038	VM440C	41068	440 Volts	Ea Pack
VM460A	41010	VM460B	41039	VM460C	41069	460 Volts	Ea Pack
VM480A	41011	VM480B	41040	VM480C	41070	480 Volts	Ea Pack
VM550A	41012	VM550B	41041	VM550C	41071	550 Volts	Ea Pack
VM600A	41013	VM600B	41042	VM600C	41072	600 Volts	Ea Pack
VM2200A	41014	VM2200B	41043	VM2200C	41073	2200 Volts	Ea Pack
VM2300A	41015	VM2300B	41044	VM2300C	41074	2300 Volts	Ea Pack
VM2400A	41016	VM2400B	41045	VM2400C	41075	2400 Volts	Ea Pack
VM4160A	41017	VM4160B	41046	VM4160C	41076	4160 Volts	Ea Pack
VM4800A	41018	VM4800B	41047	VM4800C	41077	4800 Volts	Ea Pack
VM6900A	41019	VM6900B	41048	VM6900C	41078	6900 Volts	Ea Pack
VM7200A	41020	VM7200B	41049	VM7200C	41079	7200 Volts	Ea Pack
VM13200A	41021	VM13200B	41050	VM13200C	41080	13200 Volts	Ea Pack
VMACA	41022	VMACB	41051	VMACC	41081	AC	Ea Pack
VMDCA	41023	VMDCB	41052	VMDCC	41082	DC	Ea Pack
VM1PHA	41024	VM1PHB	41053	VM1PHC	41083	Single Phase	Ea Pack
VM3PHA	41025	VM3PHB	41054	VM3PHC	41084	Three Phase	Ea Pack
VMPWA	41026	VMPWB	41055	VMPWC	41085	Power	Ea Pack
VMCBA	41027	VMCBB	41056	VMCBC	41086	Circuit Breaker	Ea Pack
VMFBA	41028	VMFBB	41057	VMFBC	41087	Fuse Box	Ea Pack

STYLE A 2.25" x 9"



STYLE B 1.125" x 4.5"



STYLE C .5" x 2.25"




Temperature Range - 40° F to 250° F
Adhesion: 45 oz./in. width ultimate

All Legends are black type on orange background.
Weight per standard pack 0.05#



- Vinyl Cloth Resists Dirt, Etc.
- Non Smearing Quality Print
- High Tack Acrylic Adhesive
- Temperature Range -40° F. to 250° F
- Pocket Sized 1-1/4" Perforated

Wire Marker / Circuit Breaker Books are available in a combination of industry recognized numbers, letters, Nema colors and legends. They eliminate costly trial and error searches.



CAT NO	UPC	LEGEND	QTY. OF MARKERS	STD	MSTR	WT/STD	UNIT
DM09	16300	0-9	60 Ea, 0-4 / 30 Ea, 5-9	1	10	.09#	Ea
DM145	16302	1-45	10 Each	1	10	.09#	Ea
DM4690	16304	46-90	10 Each	1	10	.09#	Ea
DMAZ	16306	A-Z, 0-15, +,-,/	10 Each	1	10	.09#	Ea
DMNC	16329	10 NEMA Colors	10 Each	1	10	.09#	Ea
DMBA	16327	Burglar/Security Alarm	3 Sets of 90	1	10	.09#	Ea
DMFA	16328	Fire/Security Alarm	3 Sets of 90	1	10	.09#	Ea

Circuit Breaker Marker Books

DMCM	67597	Residential Markers	3 sets of 90 Markers	1	10	.09#	Ea
------	-------	---------------------	----------------------	---	----	------	----

Each book consists of 3 sets of 90 different legends such as: main, kitchen outlets, bedroom outlets, heating, laundry, patio, etc. Covers almost every residential need.

Wire Terminal Kit | PC 5370

- UL Listed
- Pure Copper
- One Piece Burr Free Construction
- Crimped Serrations Grip Wire
- Visual Open Barrel
- Wire Range Imprinted
- Color Coded Insulation
- Made in USA



CAT NO	UPC	DESCRIPTION	STD	MSTR	WT/STD	UNIT
TK250	11554	250 pc. Assortment Kit	1	10	.88#	Ea

Lumber Crayon | PC 6630

- Lead Free
- Weather Resistant
- Fade Resistant

Lumber crayons are used to write on cardboard, concrete, lumber (rough or smooth), metal, paper, plastic, etc. Now in a 3 pack by color.



CAT NO	UPC	DESCRIPTION	COLOR	STD	MSTR	WT/STD	UNIT
DCR3P	67561	3 Red Lumber Crayons	Red	1	10	0.230#	Ea Pack
DCY3P	67571	3 Yellow Lumber Crayons	Yellow	1	10	0.230#	Ea Pack
DCB3P	67576	3 Blue Lumber Crayons	Blue	1	10	0.230#	Ea Pack
DCBLK3P	67566	3 Black Lumber Crayons	Black	1	10	0.230#	Ea Pack
DCB	14650	54 Blue Lumber Crayons	Blue	54	540	1.100#	Ea Pc.

Lumber Crayon Holder

DCH	67585	Lumber Crayon Holder	Walnut	1	6	0.050#	Ea
-----	-------	----------------------	--------	---	---	--------	----

