

Milwaukee[®]

Nothing but **HEAVY DUTY.**[®]

M12 SYSTEM **M18** SYSTEM

2017 CORDLESS CATALOG



THE WORLD LEADER IN CORDLESS INNOVATION



DEDICATION TO THE TRADES

Since the company began in 1924, Milwaukee Tool has led the industry in both durability and performance. With an unwavering commitment to the trades, MILWAUKEE® continues to lead with a focus on providing innovative, cordless, trade-specific solutions. MILWAUKEE® is dedicated to delivering a steady stream of advanced solutions for the trades that offer increased productivity and unmatched durability.

GAME-CHANGING SOLUTIONS

At MILWAUKEE®, the phrase “good enough” doesn’t exist in our vocabulary. Our goal is to solve problems in ways that have never been done before. The result: tools that offer unmatched levels of performance, productivity and durability.



BUILT ON THE BEST FOUNDATION




REDLITHIUM™ BATTERIES

They last longer, think faster and work harder than all other professional LITHIUM-ION batteries. Built to withstand even the harshest environments, REDLITHIUM™ batteries deliver more work over the life of the battery, no matter what the job.



MILWAUKEE® HIGH PERFORMANCE MOTORS

Highly advanced motor technology boosts efficiency, generating more power from a compact power source. That means the ultimate performance, durability and run-time comes in a smaller, lighter package.



REDLINK™ INTELLIGENCE

An advanced combination of hardware and software, REDLINK™ Intelligence enables full-circle communication between our batteries and tools, allowing for unmatched levels of performance, protection and productivity.

USER-DRIVEN INNOVATIONS

Our mission in cordless design is to introduce new solutions that make tradesmen more productive on the jobsite. Working side by side with users during the design and testing process gives us the ability to deliver game-changing solutions. Whether it's bringing cordless power to traditionally corded products and manual activities, or advances to fundamental tools, our drive to improve workplace productivity continues to help us push the envelope in innovation and design.

**M18™ FORCE LOGIC™
10 Ton Knockout Tool
THE EASIEST
WAY TO PUNCH**

The MILWAUKEE® Knockout System makes every step in the hole making process both faster and easier. The EXACT™ punches and dies are set up separately from the tool for extreme ease of use, utilizing a quick connect alignment system that allows the user to snap the tool onto the punches and dies without fighting against its weight, and pull the trigger to punch the hole with ease.



M18 FUEL™ 10" Dual Bevel Sliding Compound Miter Saw

5 3/4" VERTICAL **CORDED** **OVER 400 CUTS**
2x12 HORIZONTAL **PERFORMANCE** **ONE M18™ PACK**

The M18 FUEL™ 10" Dual Bevel Sliding Compound Miter Saw is designed to meet the demanding needs of professional carpenters and remodelers. Delivering greater capacity than many corded 10" sliding miter saws and corded cutting performance with the POWERSTATE™ Brushless Motor. The M18 FUEL™ 10" Dual Bevel Sliding Compound Miter Saw provides users a solution to replace their corded miter saws. The M18™ REDLITHIUM™ HIGH DEMAND™ 9.0 Battery pack delivers over 400 cuts per charge, making the saw capable of lasting an entire day on site with only one pack.

M18 FUEL™ 1-9/16" SDS Max Rotary Hammer

AS FAST AS CORDED **CORDED DURABILITY** **OVER 20 MIN OF CHIPPING**

The M18 FUEL™ 1-9/16" SDS Max Rotary Hammer is the first SDS Max 18V cordless solution. By utilizing proprietary M18 FUEL™ technologies, the 1-9/16" SDS Max rotary hammer is able to drill as fast as a corded SDS Max rotary hammer, deliver corded durability and provide over 20 minutes of continuous chipping.



M18 FUEL™ SUPER HAWG™ 1/2" Right Angle Drill

POWERS THROUGH 6" HOLES **OVER 150 2-9/16" HOLES PER CHARGE** **CORDLESS ROUGH-INS**

The first cordless tool of its kind, the M18 FUEL™ SUPER HAWG™ delivers the power and run-time to complete full cordless rough-ins. Optimized for large-diameter hole drilling, the M18 FUEL™ SUPER HAWG™ powers through 6" holes and has the ability to drill over (150) 2-9/16" holes per charge. The QUIK-LOK™ chuck provides quick, one-handed bit changes, eliminating downtime and increasing productivity.

M18 FUEL™ 1-1/2" Magnetic Drill

FASTER THAN CORDED **STRONGEST MAGNETIC HOLD ON 1/4" STEEL** **76 13/16" HOLES PER CHARGE**

The M18 FUEL™ Magnetic Drill delivers performance and run-time expected by corded magnetic drill users. This tool utilizes permanent magnets to ensure the magnetic base does not deactivate even if the battery is drained. The M18 FUEL™ Magnetic Drill also delivers the strongest magnetic hold on 1/4" steel and a magnetic base that operates without electricity, providing a safer drilling environment on 1/4" steel.



**M18™ ROCKET™ LED Tower Light/Charger
STAND UP. LIGHT UP. CHARGE UP.**

The M18™ ROCKET™ LED Tower Light/Charger is designed to deliver a lighting solution that ADAPTS, PERFORMS and SURVIVES professional use unlike any other portable work light. The light head can be extended from 4' – 7' to light overhead work or minimize shadows when casting light downward. The multidirectional light head gives users the ability to orient the three independently pivoting light heads to cast light in several directions. With an integrated AC plug, a user can plug in the light with a standard extension cord and charge any M18™ REDLITHIUM™ pack.




HIGH PERFORMANCE MOTORS

The MILWAUKEE® POWERSTATE™ Brushless Motor converts energy into power and torque more efficiently, resulting in superior application performance. The POWERSTATE™ Brushless Motor has nearly 4X the amount of power-generating components than the competitor's brushless motor. It also features higher-grade, rare-earth magnets and greater copper content.



LONGER MOTOR LIFE | MORE POWER | MORE RUN-TIME



REDLINK™ INTELLIGENCE

REDLINK™ Intelligence is an advanced combination of hardware and software that delivers the precise amount of power and performance necessary for the application, leaving your investment better protected and more productive.

UNMATCHED PROTECTION | OPTIMIZED PERFORMANCE | MORE PRODUCTIVITY

OVERLOAD PROTECTION



Best-in-class, advanced overload protection from MILWAUKEE® delivers maximum performance and protection.

OPTIMIZED PERFORMANCE



Every tool has its own unique performance profile. REDLINK™ Intelligence optimizes performance for each MILWAUKEE® tool, taking into account the specific hardware, its application and the loads placed on it.

MORE PRODUCTIVITY



All MILWAUKEE® cordless tools feature a fuel gauge. This allows tradesmen to monitor remaining battery power prior to starting a job.

REDLINK PLUS™ INTELLIGENCE

REDLINK PLUS™ delivers more advanced communication between the tool, battery and charger, resulting in peak application performance and protection. The upgraded electronics allow for new feature sets like DRIVE CONTROL™, which allows tradesmen to go from precision work to maximum performance with the push of a button.




Proprietary 4-Mode DRIVE CONTROL™

SHATTERING CORDLESS EXPECTATIONS


BATTERY TECHNOLOGY

Since introducing the world's first LITHIUM-ION cordless system in 2005, MILWAUKEE® has continued to lead the industry in LITHIUM-ION technology and patents. MILWAUKEE's focus on LITHIUM-ION continually drives the company ahead of the competition to deliver the best battery systems in the industry. The exclusive integration of chemistry, pack design and circuitry combines for superior output in the harshest environments.


MORE POWER | MORE RUN-TIME | LONGER BATTERY LIFE




- Water Protection Barrier**
 - Routes water away from the electronics and out of the battery pack
- REDLINK™ Electronics**
 - Full M18™ System compatibility
 - Protection from abuse
 - Optimum tool and pack performance
- Temp Control Frame**
 - Extends run-time and life by minimizing heat
 - Operates below -18°C / 0°F
- Fully Enclosed Cell Carrier & Rubber Overmold**
 - Prevents pack failure from vibration or drops



MORE POWER



MORE RUN-TIME



LONGER BATTERY LIFE



ONE-KEY™

UNLOCKING THE DIGITAL JOBSITE.™



DIGITAL PLATFORM FOR TOOLS & EQUIPMENT



CUSTOMIZE. TRACK. MANAGE.



Customize your tool by dialing in performance.



Track your tool's location from anywhere.



Lock your tool and disable remotely.



Manage your inventory your way.

See pages 31, 35 – 36, 39, 45 – 47 and 50 for ONE-KEY™ Compatible Tools



TICK™

TRACKS ANYTHING.
SURVIVES EVERYTHING.
TOOL AND EQUIPMENT TRACKER



Map Data ©2017 Google.

RUGGED PROTECTION



AVAILABLE KITS

1 PK TICK™ Tool and Equipment Tracker 48-21-2000
Includes: CR 2032 Coincell Battery

10 PK TICK™ Tool and Equipment Tracker 48-21-2010
Includes: (10) CR 2032 Coincell Batteries

4 PK TICK™ Tool and Equipment Tracker 48-21-2004
Includes: (4) CR 2032 Coincell Batteries

50 PK TICK™ Tool and Equipment Tracker 48-21-2050
Includes: (50) CR 2032 Coincell Batteries

Apple, the Apple logo and iBeacon are trademarks of Apple Inc., registered in the U.S. and other countries. App Store is a service mark of Apple Inc. Google Play and the Google Play logo are trademarks of Google Inc.

TRACKED BY ONE-KEY™




Learn More:
milwaukeetool.com/one-key

DOWNLOAD THE FREE APP NOW!



ONE-KEY™



M12

**PORTABLE
PRODUCTIVITY**



DRIVEN TO OUTPERFORM.™

M12 FUEL™ is engineered for the most demanding tradesmen in the world. M12 FUEL™ delivers unrivaled performance in a compact structure and features three MILWAUKEE® exclusive innovations—the POWERSTATE™ Brushless Motor, REDLITHIUM™ Battery Pack and REDLINK PLUS™ Intelligence Hardware and Software—that deliver unmatched power, run-time and durability.

Simply put, M12 FUEL™ is best-in-class, full-circle technology that drives, protects and powers your cordless tools beyond the rest.

M12 FUEL

LONGER MOTOR LIFE | **MORE** POWER | **MORE** RUN-TIME

NOW AVAILABLE




UPGRADE.
OUTWORK. OUTLAST.

UP TO **3X** MORE RUN-TIME | UP TO **20%** MORE POWER | OVER **2X** MORE LIFE


1 POWERSTATE™ BRUSHLESS MOTOR

- MILWAUKEE® Designed and Built Brushless Motor
- Outperforms All Leading Competitors
- Up to 10X Longer Motor Life



2 REDLINK PLUS™ INTELLIGENCE

- Most Advanced Electronic System on the Market for Maximum Performance
- Total System Communication with Overload Protection Increases Tool Life
- Built-In Fuel Gauge Displays Remaining Charge




3 REDLITHIUM™ 3.0 & XC6.0 BATTERY PACKS

- Up to 3X More Run-Time
- Up to 20% More Power
- Over 2X More Recharges than Leading Competitors
- Operates Below -18°C / 0°F



5
YEAR WARRANTY



M12
SYSTEM

M12 FUEL
1/4" Hex 2-Speed Screwdriver Kit

2402-22 (2402-20 Tool-Only)

Specifications:

Peak Torque	325 in-lbs
RPM	0 – 450 / 0 – 1,700
Chuck Type	1/4" Hex Quick Change
Length	6-5/8"
Weight	2.3 lbs

Includes: (2) M12™ REDLITHIUM™ 2.0 Compact Battery Packs, Belt Clip, Charger, Carrying Case



M12™ 3/8" Hammer Drill/Driver Kit

2408-22 (2408-20 Tool-Only)

Specifications:

Peak Torque	275 in-lbs
RPM	0 – 400 / 0 – 1,500
BPM	0 – 22,500
Chuck Type	3/8" Metal Single Sleeve
Length	7-1/2"
Weight	2.7 lbs

Includes: (2) M12™ REDLITHIUM™ Compact Battery Packs, Belt Clip, Charger, Carrying Case



M12™ 1/4" Hex Impact Driver Kit

2462-22 (2462-20 Tool-Only)

Specifications:

Fastening Torque	1,000 in-lbs
IPM	0 – 3,300
RPM	0 – 2,500
Chuck Type	1/4"
Length	6-1/2"
Weight	2.3 lbs

Includes: (2) M12™ REDLITHIUM™ Compact Battery Packs, Belt Clip, Charger, Carrying Case



M12™ 1/4" Hex 2-Speed Screwdriver Kit

2406-22 (2406-20 Tool-Only)

Specifications:

Peak Torque	275 in-lbs
RPM	0 – 400 / 0 – 1,500
Chuck Type	1/4" Hex Quick Change
Length	6-3/4"
Weight	2.2 lbs

Includes: (2) M12™ REDLITHIUM™ Compact Battery Packs, Belt Clip, Charger, Carrying Case



M12 FUEL
1/2" Drill/Driver Kit

2403-22 (2403-20 Tool-Only)

Specifications:

Peak Torque	350 in-lbs
RPM	0 – 450 / 0 – 1,700
Chuck Type	1/2" Metal Single Sleeve – Ratcheting Chuck
Length	7-3/4"
Weight	2.9 lbs

Includes: (1) M12™ REDLITHIUM™ XC4.0 Extended Capacity Battery Pack, (1) M12™ REDLITHIUM™ 2.0 Compact Battery Pack, Belt Clip, Charger, Carrying Case



M12™ 1/4" Hex Right Angle Impact Driver Kit

2467-21 (2467-20 Tool-Only)

Specifications:

Fastening Torque	600 in-lbs
RPM	0 – 2,450
IPM	0 – 3,300
Chuck Type	1/4" Hex
Head Profile	1.4" Diameter
Weight	2.6 lbs

Includes: (1) M12™ REDLITHIUM™ Compact Battery Pack, Charger, Soft Carrying Case



M12™ 1/4" Impact Wrench Kit

2461-22 (2461-20 Tool-Only)

Specifications:

Fastening Torque	38 ft-lbs
IPM	0 – 3,800
RPM	0 – 2,500
Anvil	1/4" Friction Ring
Length	6"
Weight	2.1 lbs

Includes: (2) M12™ REDLITHIUM™ Compact Battery Packs, Belt Clip, Charger, Carrying Case



M12™ 1/4" Hex Screwdriver Kit

2401-22 (2401-20 Tool-Only)

Specifications:

Peak Torque	175 in-lbs
RPM	0 – 500
Chuck Type	1/4" Hex Quick Change
Length	6-1/2"
Weight	2.0 lbs

Includes: (2) M12™ REDLITHIUM™ Compact Battery Packs, Belt Clip, Charger, Soft Carrying Case



M12™ 3/8" Drill/Driver Kit

2407-22 (2407-20 Tool-Only)

Specifications:

Peak Torque	275 in-lbs
RPM	0 – 400 / 0 – 1,500
Chuck Type	3/8" Metal Single Sleeve
Length	7-3/8"
Weight	2.5 lbs

Includes: (2) M12™ REDLITHIUM™ Compact Battery Packs, Belt Clip, Charger, Carrying Case



M12 FUEL
3/8" Impact Wrench Kit

2454-22 (2454-20 Tool-Only)

Specifications:

Fastening Torque (2-Mode)	17 / 117 ft-lbs
IPM	0 – 3,500
RPM (2-Mode)	0 – 1,200 / 0 – 2,650
Anvil	3/8" Friction Ring
Length	6-1/2"
Weight	2.4 lbs

Includes: (2) M12™ REDLITHIUM™ 2.0 Compact Battery Packs, Belt Clip, Charger, Carrying Case



M12™ 3/8" Right Angle Drill/Driver Kit

2415-21 (2415-20 Tool-Only)

Specifications:

Peak Torque	100 in-lbs
RPM	0 – 800
Clutch Settings	11 Settings plus Drill Mode
Chuck Type	3/8" Single Sleeve
Head Profile	3-3/4"
Weight	2.4 lbs

Includes: (1) M12™ REDLITHIUM™ Compact Battery Pack, Charger, Soft Carrying Case



M12™ 3/8" Impact Wrench Kit

2463-22 (2463-20 Tool-Only)

Specifications:

Fastening Torque	100 ft-lbs
IPM	0 – 3,300
RPM	0 – 2,500
Chuck Type	3/8" Friction Ring
Length	6-1/2"
Weight	2.3 lbs

Includes: (2) M12™ REDLITHIUM™ Compact Battery Packs, Belt Clip, Charger, Carrying Case



M12™ 3/8" Ratchet Kit

2457-21 (2457-20 Tool-Only)

Specifications:

Fastening Torque	35 ft-lbs
RPM	0 – 250
Anvil	3/8" Ball Detent
Head Profile	3/4"
Length	10-3/4"
Weight	1.9 lbs

Includes: (1) M12™ REDLITHIUM™ Compact Battery Pack, 3/8" to 1/4" Adapter, Charger, Soft Carrying Case



M12 FUEL
1/2" Hammer Drill/Driver Kit

2404-22 (2404-20 Tool-Only)

Specifications:

Peak Torque	350 in-lbs
RPM	0 – 450 / 0 – 1,700
BPM	0 – 25,500
Chuck Type	1/2" Metal Single Sleeve – Ratcheting Chuck
Length	7-3/4"
Weight	3.0 lbs

Includes: (1) M12™ REDLITHIUM™ XC4.0 Extended Capacity Battery Pack, (1) M12™ REDLITHIUM™ 2.0 Compact Battery Pack, Belt Clip, Charger, Carrying Case



M12 FUEL
1/4" Hex Impact Driver Kit

2453-22 (2453-20 Tool-Only)

Specifications:

Fastening Torque (2-Mode)	175 / 1,200 in-lbs
IPM	0 – 3,550
RPM (2-Mode)	0 – 1,200 / 0 – 2,650
Chuck Type	1/4" Hex Quick Change
Length	6"
Weight	2.3 lbs

Includes: (2) M12™ REDLITHIUM™ 2.0 Compact Battery Packs, Belt Clip, Charger, Carrying Case



M12 FUEL
1/4" Impact Wrench Kit

2452-22 (2452-20 Tool-Only)

Specifications:

Fastening Torque (2-Mode)	10 / 42 ft-lbs
IPM	0 – 4,000
RPM (2-Mode)	0 – 1,200 / 0 – 2,650
Anvil	1/4" Friction Ring
Length	5-3/4"
Weight	2.1 lbs

Includes: (2) M12™ REDLITHIUM™ 2.0 Compact Battery Packs, Belt Clip, Charger, Carrying Case



M12™ 1/4" Ratchet Kit

2456-21 (2456-20 Tool-Only)

Specifications:

Fastening Torque	30 ft-lbs
RPM	0 – 250
Anvil	1/4" Ball Detent
Head Profile	3/4"
Length	10-3/4"
Weight	1.9 lbs

Includes: (1) M12™ REDLITHIUM™ Compact Battery Pack, Charger, Soft Carrying Case




M12 FUEL 5/8" SDS Plus Rotary Hammer Kit
2416-22XC (2416-20 Tool-Only)

Specifications:

RPM	0 – 900
BPM	0 – 6,200
2-Mode Operation	Rotary Hammer and Rotation Only
Length	10"
Weight	3.9 lbs

Includes: (2) M12™ REDLITHIUM™ XC4.0 Extended Capacity Battery Packs, Charger, Carrying Case

Related Accessory:
2306-22 M12™ HAMMERVAC™ Universal Dust Extractor





M12™ 1/2" SDS Plus Rotary Hammer Kit
2412-22XC (2412-20 Tool-Only)

Specifications:

RPM	0 – 800
BPM	0 – 5,350
2-Mode Operation	Rotary Hammer and Rotation Only
Length	9"
Weight	3.9 lbs

Includes: (2) M12™ REDLITHIUM™ XC Extended Capacity Battery Packs, Charger, Carrying Case

Related Accessory:
2306-22 M12™ HAMMERVAC™ Universal Dust Extractor




M12™ Palm Nailer Kit
2458-21 (2458-20 Tool-Only)

Specifications:

Impact Energy	2.2 ft-lbs (3.0 J)
BPM	0 – 2,700
Collet Capacity	6D – 16D
Head	3/4" Low Profile
Magnetic Tip	Yes
Weight	3.4 lbs

Includes: (1) M12™ REDLITHIUM™ Compact Battery Pack, Hand Strap, Charger, Soft Carrying Case




M12™ HAMMERVAC™ Universal Dust Extractor Kit
2306-22 (2306-20 Tool-Only)

COMPLIANCE OSHA SOLUTION **CERTIFIED HEPA FILTER**

INDUSTRY'S ONLY UNIVERSAL DUST EXTRACTOR



Specifications:

Universal Handle System	Compatible with Major Brands of SDS Plus Rotary Hammers and AC and DC Hammer Drills
Replaceable Certified HEPA Filter	Filters 99.97% of Debris 0.3 Microns and Above
Self-Powered by M12™ REDLITHIUM™ Battery Pack	No Cords or Hoses for Maximum Portability
3-Mode Switch	Yes (Auto-On and Auto-Off w/ Delay)
Max Bit Size	5/8"
Weight	3.3 lbs

Includes: (2) M12™ REDLITHIUM™ Compact Battery Packs, (3) Side Handle Collars, Side Handle Grip, Nozzle, Charger, Carrying Case




M12™ Spot Polisher Kit
2438-22X, 2438-22 (2438-20 Tool-Only)

Specifications:

Polishing RPM	0 – 2,800
Sanding RPM	0 – 8,300
Length	5-1/10"
Weight	2.4 lbs

Includes: 2438-22X (1) M12™ REDLITHIUM™ XC Extended Capacity Battery Pack, (1) M12™ REDLITHIUM™ Compact Battery Pack, 5 Pc Accessory Pack, Side Handle, Charger, Soft Carrying Case; 2438-22 Includes (2) M12™ REDLITHIUM™ Compact Battery Packs



M12 FUEL 5-3/8" Circular Saw Kit
2530-21XC (2530-20 Tool-Only)

Specifications:

RPM	3,600
Bevel Capacity	50°
Cut Capacity	1-5/8" at 90°; 1-1/8" at 45°
Arbor	10 mm
Blade Guards	Aluminum
Weight	6.2 lbs

Includes: (1) M12™ REDLITHIUM™ XC4.0 Extended Capacity Battery Pack, Circular Saw Blade, Wrench, Charger, Contractor Bag




M12 FUEL HACKZALL® Recip Saw Kit
2520-21XC (2520-20 Tool-Only)

Specifications:

SPM	0 – 3,000
Stroke Length	5/8"
Keyless Blade Clamp	QUIK-LOK™ (Accepts all SAWZALL® Blades)
Length	13-1/4"
Weight	4.1 lbs

Includes: (1) M12™ REDLITHIUM™ XC4.0 Extended Capacity Battery Pack, HACKZALL® Blade, Charger, Contractor Bag




M12™ HACKZALL® Recip Saw Kit
2420-22, 2420-21 (2420-20 Tool-Only)

Specifications:

SPM	0 – 3,000
Stroke Length	1/2"
Keyless Blade Clamp	QUIK-LOK™ (Accepts all SAWZALL® Blades)
Length	11"
Weight	2.6 lbs

Includes: 2420-22 (2) M12™ REDLITHIUM™ Compact Battery Packs, (2) HACKZALL® Blades, Charger, Contractor Bag; 2420-21 Includes (1) M12™ REDLITHIUM™ Compact Battery Pack




M12™ High Performance Jig Saw Kit
2445-21 (2445-20 Tool-Only)

Specifications:

SPM	0 – 2,800
Stroke Length	3/4"
Bevel Capacity	45° (Positive Locks at 90° and 45°)
Blade Clamp	QUIK-LOK™ T-Shank
Length	8-3/4"
Weight	4.2 lbs

Includes: (1) M12™ REDLITHIUM™ Compact Battery Pack, MILWAUKEE® 10 TPI Wood Cutting T-Shank Jig Saw Blade, Anti-Splintering Insert, Non-Marring Shoe, Charger, Contractor Bag



M12™ Multi-Tool Kit
2426-22, 2426-21 (2426-20 Tool-Only)

Specifications:

Speed Settings	12
OPM	5,000 – 20,000
Universal Accessory Adapter	Yes
Length	10-7/8"
Weight	2.1 lbs

Includes: 2426-22 (2) M12™ REDLITHIUM™ Compact Battery Packs, Accessory Adapter, Wood Cutting Blade, Sanding Pad, (5) Assorted Sanding Sheets, Charger, Contractor Bag; 2426-21 Includes (1) M12™ REDLITHIUM™ Compact Battery Pack



M12™ Sub-Compact Band Saw Kit
2429-21XC (2429-20 Tool-Only)

Specifications:

SFPM	280
Blade Size	27"
Cut Capacity	1-5/8" x 1-5/8"
Length	11"
Weight	6.7 lbs

Includes: (1) M12™ REDLITHIUM™ XC Extended Capacity Battery Pack, 18 TPI Sub-Compact Portable Band Saw Blade, Charger, Carrying Case

Related Accessory:
48-39-0572 18 TPI Sub-Compact Portable Band Saw Blades (3-Pack)

Meets OSHA Guarding Requirements. Suitable for One-Handed Use.




M12™ Plastic Pipe Shear Kit

2470-21 (2470-20 Tool-Only)

Specifications:

Cut Capacity	Up to 2" Schedule 80 PVC
Torque	1,900 in-lbs
Blade	3 mm Reinforced Stainless Steel
Length	14-3/8"
Weight	4.35 lbs



Includes: (1) M12™ REDLITHIUM™ Compact Battery Pack, Charger, Carrying Case

Related Accessory:
48-44-0405 M12™ Plastic Pipe Shear Blade



M12™ Copper Tubing Cutter Kit

2471-22, 2471-21 (2471-20 Tool-Only)

Specifications:

Cut Capacity	3/8" – 1" (1/2" – 1-1/8" O.D.)
Tubing Type	M, L and K Copper
RPM	500
Length	14"
Weight	3.2 lbs



Includes: 2471-22 (2) M12™ REDLITHIUM™ Compact Battery Packs, Charger, Carrying Case; 2471-21 Includes (1) M12™ REDLITHIUM™ Compact Battery Pack

Related Accessory:
48-38-0010 Copper Cutter Wheel (2-Pack)

M12™ Rotary Tool Kit

2460-21 (2460-20 Tool-Only)

Specifications:

Speed Settings	6
RPM	5,000 – 32,000
Collet	1/8", Universal
Length	9-1/2"
Weight	1.3 lbs



Includes: (1) M12™ REDLITHIUM™ Compact Battery Pack, (5) Cutting Wheels, Mandrel, Wrench, Charger, Soft Carrying Case

Related Accessory:
49-94-1500 5 Pc Reinforced Cut-Off Wheels

M12™ 600 MCM Cable Cutter Kit

2472-21XC (2472-20 Tool-Only)

Specifications:

Cut Capacity	600 MCM Copper, 750 MCM Aluminum, 1-3/16" Communication Cable
Jaw Opening	1-7/16"
Two-Speed	Yes
Length	10-1/2"
Weight	6.7 lbs



Includes: (1) M12™ REDLITHIUM™ XC Extended Capacity Battery Pack, Multi-Voltage Charger, Carrying Case

Related Accessory:
48-44-0410 M12™ 600 MCM Cable Cutter Blade

M12™ Drain Snake Kit

2571-21 (2571-20 Tool-Only)

Specifications:

1/4" Capacity	25'
5/16" Capacity	25'
Speed Control	0 – 500 RPM
LED Light	Yes
Weight (w/ cable)	10.6 lbs



Includes: (1) M12™ REDLITHIUM™ Compact Battery Pack, 5/16" x 25' Inner Core Bulb Head Cable with Inner Drum, Charger, 5 Gallon Storage Bucket

Related Accessories:
48-53-2571 5/16" x 25' Inner Core Bulb Head Cable;
48-53-2572 5/16" x 25' Inner Core Drop Head Cable;
48-53-2573 1/4" x 25' Inner Core Bulb Head Cable;
48-53-2574 1/4" x 25' Inner Core Drop Head Cable;
48-53-2581 5/16" x 25' Inner Core Bulb Head Cable w/ Drum;
48-53-2582 5/16" x 25' Inner Core Drop Head Cable w/ Drum;
48-53-2583 1/4" x 25' Inner Core Bulb Head Cable w/ Drum;
48-53-2584 1/4" x 25' Inner Core Drop Head Cable w/ Drum



M12™ TRAPSSNAKE™ 6' Toilet Auger Kit

2576-21 (2576-20 Tool-Only)

Specifications:

RPM	0 – 500
Cable Lock	Yes
Cable Size	6' x 1/2"
Cable Head	Retriever Bulb
Replacement Cables	Available
Weight	9.0 lbs



Includes: (1) M12™ REDLITHIUM™ Compact Battery Pack, Cable, Charger

Related Accessory:
48-53-2576 TRAPSSNAKE™ 6' Toilet Auger Replacement Cable

M12™ TRAPSSNAKE™ 4' Urinal Auger Kit

2574-21 (2574-20 Tool-Only)

Specifications:

RPM	0 – 500
Cable Lock	Yes
Cable Size	4' x 3/8"
Cable Head	Bulb
Replacement Cables	Available
Weight	6.4 lbs



Includes: (1) M12™ REDLITHIUM™ Compact Battery Pack, Cable, Charger

Related Accessory:
48-53-2577 TRAPSSNAKE™ 4' Urinal Auger Replacement Cable

M12™ ProPEX® Expansion Tool Kit

2432-22XC, 2432-22 (2432-20 Tool-Only)

Specifications:

Capacity	3/8" – 1"
Auto-Rotate	Built-In
Head Compatibility	3/8" – 1" M12™ / Uponor
Dimensions (L x W x H)	7-1/10" x 3-7/10" x 12-4/5"
Weight	5.0 lbs



Includes: 2432-22 XC (2) M12™ REDLITHIUM™ XC Extended Capacity Battery Packs, (3) ProPEX® Expansion Heads (1/2", 3/4", 1"), Grease, Charger, Carrying Case; 2432-22 Includes (2) M12™ REDLITHIUM™ Compact Battery Packs

Related Accessories:

49-16-2403 3/8" ProPEX® Expansion Head;
49-16-2404 1/2" ProPEX® Expansion Head;
49-16-2405 5/8" ProPEX® Expansion Head;
49-16-2406 3/4" ProPEX® Expansion Head;
49-16-2408 1" ProPEX® Expansion Head

M12™ FORCE LOGIC™ Press Tool Kit

2473-22 (2473-20 No Jaw Kit)

Specifications:

Capacity	1/2" – 1-1/4" CU
Calibration Interval	32,000 Cycles (LED Indicator)
Approximate Cycle Time	5 Seconds
Press Force	5,400 lbs
Length	12-3/4"
Weight	3.8 lbs



Includes: 2473-22 (2) M12™ REDLITHIUM™ Compact Battery Packs, (3) Jaws (1/2", 3/4", 1"), Charger, Carrying Case; 2473-20 Includes No Jaws

Related Accessories:

49-16-2450 M12™ 1/2" Jaw;
49-16-2451 M12™ 3/4" Jaw;
49-16-2452 M12™ 1" Jaw;
49-16-2453 M12™ 1-1/4" Jaw



M12™ No-Hub Driver Kit

2455-22 (2455-20 Tool-Only)

Specifications:

Torque Settings (3-Mode)	60 in-lbs / 80 in-lbs / Drill
RPM	0 – 750
Chuck Type	1/4" Hex
Calibration Interval	25,000 Cycles (LED Indicator)
Weight	2.7 lbs



Includes: (2) M12™ REDLITHIUM™ Compact Battery Packs, (3) SHOCKWAVE™ Nut Drivers (1/4", 5/16", 3/8"), Charger, Carrying Case

M12™ 10 oz Caulk and Adhesive Gun Kit

2441-21 (2441-20 Tool-Only)

Specifications:

Force	400 lbs
Inches Per Minute	0 – 29
Speed Settings	6
Auto-Reverse Anti-Drip	Yes
Weight	4.1 lbs



Includes: (1) M12™ REDLITHIUM™ Compact Battery Pack, 10 oz Carriage, M12™ 10 oz Plunger Rod and Piston Assembly, Charger

M12™ 20 oz Aluminum Barrel Sausage Style Caulk and Adhesive Gun Kit

2442-21

Specifications:

Force	400 lbs
Inches Per Minute	0 – 29
Speed Settings	6
Auto-Reverse Anti-Drip	Yes
Weight	4.9 lbs



Includes: (1) M12™ REDLITHIUM™ Compact Battery Pack, 20 oz Aluminum Sausage Style Barrel, M12™ 20 oz Plunger Rod and Piston Assembly, Nozzle, Charger

M12™ Quart Caulk and Adhesive Gun Kit

2444-21

Specifications:

Force	400 lbs
Inches Per Minute	0 – 29
Speed Settings	6
Auto-Reverse Anti-Drip	Yes
Weight	5.5 lbs



Includes: (1) M12™ REDLITHIUM™ Compact Battery Pack, Quart Carriage, M12™ Quart Plunger Rod and Piston Assembly, Charger

M12™ Caulk Gun Accessories

Compatible with 2441-21, 2442-21, 2444-21
48-08-0900 M12™ 10 oz Caulk and Adhesive Gun Conversion Kit;
48-08-0905 M12™ 20 oz Aluminum Barrel Sausage Style Caulk and Adhesive Gun Conversion Kit;
48-08-0910 M12™ Quart Caulk and Adhesive Gun Conversion Kit;
48-08-1091 20 oz Aluminum Barrel Kit;
48-08-1096 20 oz Clear Barrel Kit;
31-12-0700 Caulk Gun Nozzle – Black

M12™ Grease Gun Kit

2446-21XC (2446-20 Tool-Only)

Specifications:

Output Pressure	Over 8,000 PSI
Run-Time	Up to 7 Grease Cartridges Per Charge
Grease Capacity	14 oz Cartridge, 16 oz Bulk, 16 oz Suction
Air Bleeder Valve	Yes
Weight	7.2 lbs



Includes: (1) M12™ REDLITHIUM™ XC Extended Capacity Battery Pack, 36" Flex Hose with Spring Guard, Grease Coupler, Charger, Carrying Case



M12™ M-SPECTOR FLEX™ 3 ft Inspection Camera Cable Kit

2315-21

Specifications:

Screen Size	3.5" High-Resolution LCD
Camera Resolution	640 x 480
Camera Head Diameter	12.5 mm (0.49")
Cable Length	3 ft
Wireless Distance	Up to 15 ft



Includes: (1) M12™ REDLITHIUM™ Compact Battery Pack, SD Card, USB Cable, Charger, Carrying Case



M12™ M-SPECTOR FLEX™ 3 ft Inspection Camera Cable w/ PIVOTVIEW™ Kit


2317-21

Specifications:

Screen Size	3.5" High-Resolution LCD
Camera Resolution	640 x 480
Camera Head Diameter	12.5 mm (0.49")
Head Movement	Up to 270° PIVOTVIEW™ Camera
Cable Length	3 ft
Wireless Distance	Up to 15 ft



Includes: (1) M12™ REDLITHIUM™ Compact Battery Pack, SD Card, USB Cable, Charger, Carrying Case



M12™ M-SPECTOR FLEX™ Inspection Camera Accessories

Compatible with 2317-21, 2316-21, 2315-21

- 48-53-0155** M-SPECTOR FLEX™ 3 ft Inspection Camera Cable w/ PIVOTVIEW™;
- 48-53-0151** M-SPECTOR FLEX™ 9 ft Inspection Camera Cable;
- 48-53-0150** M-SPECTOR FLEX™ 3 ft Inspection Camera Cable



M12™ M-SPECTOR FLEX™ 9 ft Inspection Camera Cable Kit

2316-21

Specifications:

Screen Size	3.5" High-Resolution LCD
Camera Resolution	640 x 480
Camera Head Diameter	12.5 mm (0.49")
Cable Length	9 ft
Wireless Distance	Up to 15 ft



Includes: (1) M12™ REDLITHIUM™ Compact Battery Pack, SD Card, USB Cable, Charger, Carrying Case



M12™ M-SPECTOR 360™ Rotating Inspection Scope Kit

2313-21 (2313-20 Tool-Only)

Specifications:

Screen Size	2.7" High-Resolution LCD
Display Resolution	320 x 240
Camera Head Diameter	9 mm (0.35")
Cable Length	3 ft
LED Brightness	4 LEDs, 5 Settings



Includes: (1) M12™ REDLITHIUM™ Compact Battery Pack, Hook, Magnet, Mirror Attachments, Charger, Carrying Case

M12™ M-SPECTOR 360™ 9 ft Rotating Inspection Scope Kit

2314-21

Specifications:

Screen Size	2.7" High-Resolution LCD
Display Resolution	320 x 240
Camera Head Diameter	9 mm (0.35")
Cable Length	9 ft
LED Brightness	4 LEDs, 5 Settings



Includes: (1) M12™ REDLITHIUM™ Compact Battery Pack, Hook, Magnet, Mirror Attachments, Pipe Guide, Charger, Carrying Case

M12™ M-SPECTOR 360™ Rotating Inspection Scope Accessories

Compatible with 2313-21, 2314-21

- 48-53-0112** Accessory 3-Pack (Includes Hook, Magnet, Mirror Attachments);
- 48-53-0113** Pipe Guide Accessory



M12™ 102 x 77 Infrared Camera Kit

2258-21

Specifications:

Thermal Resolution	102 x 77
Temperature Range	14°F – 626°F (-10°C – 330°C)
Screen Size	2.4" LCD
Distance-to-Spot Ratio (Center Crosshair)	83:1
Targeting Assistance	Dual Laser
Image Storage & Reporting	Yes



MILWAUKEE® Thermal Imaging Software Available Online

Includes: (1) M12™ REDLITHIUM™ Compact Battery Pack, Rubber Boot, USB Cable, SD Card, Manual, Charger, Soft Carrying Case



M12™ 160 x 120 Thermal Imager Kit

2260-21, NIST Certified 2260-21NST

Specifications:

Thermal Resolution	160 x 120
Temperature Range	14°F – 662°F (-10°C – 350°C)
Temperature Accuracy	±4° F (±2° C)
Visual Camera	Yes
Screen Size	3.5" LCD
Image Storage & Reporting	Yes



MILWAUKEE® Thermal Imaging Software Available Online

Includes: (1) M12™ REDLITHIUM™ Compact Battery Pack, Thermal Imager Report Software, SD Card, USB Cable, SD Card Reader, Quick Reference Card, Statement of Calibration, Charger, Carrying Case



M12™ 12:1 Infrared TEMP-GUN™

2278-20

Specifications:

Distance-to-Spot Ratio	12:1
Temperature Range	-22°F – 1,022°F (-30°C – 550°C)
Basic Accuracy	+/-1.8%
Max/Min/Avg/Dif	Yes
High/Low Alerts	Yes
Emissivity	Fixed, .95
Drop Test	6 ft



Battery and Charger Sold Separately

M12™ LED Metal Flashlight Kit

2355-21 (2355-20 Tool-Only)

Specifications:

Lumens	800 / 325 / 800
Modes	High, Medium, Strobe
Beam Distance	375 yd / 343 m
Beam Focus	Slide, Spot/Flood
Moisture Resistance	IP54
Structure	6000 Series Aluminum, Type II Anodize Finish
Length	9"
Weight	1.2 lbs



Includes: (1) M12™ REDLITHIUM™ Compact Battery Pack, Lanyard, Charger



M12™ LED Spot Light

2353-20

Specifications:

Lumens	750 / 400 / 750
Modes	High, Low, Strobe
Beam Distance	700 yd / 640 m
Moisture Resistance	IP54
Length	6-1/8"
Weight	1.4 lbs



Battery and Charger Sold Separately

Includes: Lanyard



M12™ LED Lantern/Flood Light

2362-20

Specifications:

Lumens	400 / 200 / 40 / 400
Modes	High, Medium, Low, Strobe
Beam Pattern	Adjustable 180° – 360°
Moisture Resistance	IP54
Hands-Free	2 Hooks for Hanging
USB Charger	2.1A USB Charging Port
Length	10-1/2"
Weight	1.0 lb



Battery and Charger Sold Separately



M12™ ROVER™ LED Flood Light

2364-20

Specifications:

Lumens	1,000 / 400 / 200
Modes	High, Medium, Low
Hands Free	Integrated Magnet, Spring Loaded Clamp
Moisture Resistance	IP54
Length	7-1/2"
Weight	2.2 lbs



Battery and Charger Sold Separately



M12™ LED Stick Light

2351-20

Specifications:

Lumens	220
Hands-Free	Multi-Position Stainless Steel Hook
Moisture Resistance	IP54
Length	9-1/4"
Weight	0.6 lbs



Battery and Charger Sold Separately

Related Accessory:

49-24-2351 M12™ Stick Light Magnet Holds light to metal surfaces for hands-free use

M12™ LED Work Light

49-24-0146

Specifications:

Lumens	100
Hands-Free	Integrated Magnet
Head Rotation	90°



Battery and Charger Sold Separately

M12™ Heated Jacket Kit

Black 201B-21 (201B-20 Jacket-Only)


Grey 201G-21 (201G-20 Jacket-Only)

Red 201R-21 (201R-20 Jacket-Only)

Camo 221C-21 (221C-20 Jacket-Only)

Specifications:

Heating Elements	5 (Chest, Back, Pockets)
Heat Settings	3 (High, Medium, Low)
Run-Time	Up to 8 Hours
Outer Material	TOUGH-SHELL™ Stretch Polyester
Wind/Water Resistant	Yes
USB Charger	2.1A
Washer/Dryer Safe	Yes



Includes: (1) M12™ REDLITHIUM™ 2.0 Compact Battery Pack, M12™ Power Source, Charger

Available Sizes: S, M, L, XL, 2X, 3X



M12™ Heated Hoodie Kit

Black 301B-21 (301B-20 Hoodie-Only)

Grey 301G-21 (301G-20 Hoodie-Only)

Red 301R-21 (301R-20 Hoodie-Only)

Specifications:

Heating Elements	3 (Chest, Back)
Heat Settings	3 (High, Medium, Low)
Run-Time	Up to 6 Hours
Outer Material	Cotton/Polyester Blend
Inner Lining	Thermal Waffle Weave
Washer/Dryer Safe	Yes



Includes: (1) M12™ REDLITHIUM™ Compact Battery Pack, M12™ Battery Holder, Charger

Available Sizes: S, M, L, XL, 2X, 3X

M12™ Heated 3-in-1 Jacket Kit*

Black 251B-21 (251B-20 3-in-1 Jacket-Only)

Specifications:

Heating Elements (in Hoodie)	3 (Chest, Back)
Heat Settings	3 (High, Medium, Low)
Run-Time	Up to 8 Hours
Outer Material	GRIDIRON™ Ripstop Polyester
Wind/Water Resistant	Yes
USB Charger	2.1A
Washer/Dryer Safe	Yes



Includes: (1) M12™ REDLITHIUM™ 2.0 Compact Battery Pack, M12™ Power Source, Charger

Available Sizes: S, M, L, XL, 2X, 3X
*M12™ Heated 3-in-1 Jacket is made up of (2) pieces: heated hoodie and durable outer shell.



M12™ Heated Vest Kit

Black 271B-21 (271B-20 Vest-Only)

Specifications:

Heating Elements	3 (Chest, Back)
Heat Settings	3 (High, Medium, Low)
Run-Time	Up to 6 Hours
Outer Material	GRIDIRON™ Ripstop Polyester
Inner Lining	Thermal Fleece
Wind/Water Resistant	Yes
Washer/Dryer Safe	Yes



Includes: (1) M12™ REDLITHIUM™ Compact Battery Pack, M12™ Battery Holder, Charger

Available Sizes: S, M, L, XL, 2X, 3X

M12™ Women's Heated Jacket Kit

Black 231B-21

Specifications:

Heating Elements	4 (Back, Collar, Pockets)
Heat Settings	3 (High, Medium, Low)
Run-Time	Up to 8 Hours
Outer Material	Polyester Soft Shell
Wind/Water Resistant	Yes
USB Charger	2.1A
Washer/Dryer Safe	Yes



Includes: (1) M12™ REDLITHIUM™ 2.0 Compact Battery Pack, M12™ Power Source, Charger

Available Sizes: S, M, L, XL, 2X


M12™ Heated Gear Accessory

Compatible with all M12™ Heated Gear

49-24-2301 M12™ Heated Jacket 12V DC Plug Adapter



Realtree Xtra © and Realtree MAX-1 © 2017 of Jordan Outdoor Enterprises, Ltd., all rights reserved



M12™ Power Source

49-24-2310

Specifications:

2.1 Amp USB Port	Universal Charging for Smartphones, Tablets and Other Portable Electronic Devices
On-Board Fuel Gauge	Yes
Powered By	All M12™ Batteries



Battery Sold Separately

Powers all MILWAUKEE® M12™ Heated Gear



M12™ Compact Vacuum

0850-20

Specifications:

Air Volume	33 CFM
Suction (H ₂ O)	14.5"
Run-Time	Up to 29 mins (XC4.0 Battery)
Inlet Diameter	1-1/4"
Weight	2.3 lbs



Battery and Charger Sold Separately

Includes: Utility Nozzle, Extension Wand, Crevice Tool, Filter Assembly

Related Accessory:
49-90-1950 Filter

M12™ Wireless Jobsite Speaker

2592-20

Specifications:

Modes	Bluetooth®, AUX (Cable Not Included)
Bluetooth Antenna	30 ft Range
USB Charging Port	2.1 Amps
Powered By	All M12™ Batteries



Battery and Charger Sold Separately

M18™ / M12™ Wireless Jobsite Speaker

2891-20

Specifications:

Modes	Bluetooth, AUX (Cable Not Included)
Bluetooth Range	100 ft
USB Charging Port	2.1 Amp
Powered By	All M18™ and M12™ Batteries



Battery and Charger Sold Separately

Includes: AC Adapter

M12™ Jobsite Radio

2590-20

Specifications:

Modes	AM, FM, AUX
Tuner	Digital Processor w/ 10 Station Presets
Powered By	All M12™ Batteries, AC Adapter



Battery and Charger Sold Separately

Includes: Auxiliary Input Cord, AC Adapter, (2) AAA Batteries (For Memory Backup)

M18™ and M12™ Rapid Charge Station

48-59-1807

Specifications:

Compatibility	All M18™ and M12™ Batteries
Charge Sequence	Charges 3 Batteries Simultaneously
Charge Speed	Charges Individual Batteries up to 40% Faster
Capacity	Holds (3) M18™ and (3) M12™ Batteries
Integrated Hang-Holes	Yes
Cell Voltage Monitoring	Yes
Pass-Through Plug	Yes



M18™ and M12™ Rapid Charger

48-59-1808

Specifications:

Compatibility	All M18™ and M12™ Batteries
Charge Sequence	Sequential (First In, First Charged)
Charge Speed	Charges Individual Batteries up to 40% Faster
On-Board Indicator Light	Yes
Integrated Hang-Holes	Yes
Cell Voltage Monitoring	Yes



Batteries Sold Separately

M12™ Four Bay Sequential Charger

48-59-1204

Specifications:

Compatibility	All M12™ Batteries
Charge Sequence	Sequential (First In, First Charged)
Integrated Hang-Holes	Yes
Skip Button	Manually Designate which Battery Charges First
On-Board Indicator Light	Yes
Cell Voltage Monitoring	Yes



Batteries Sold Separately

M18™ and M12™ Multi-Voltage Charger

48-59-1812

Specifications:

Compatibility	All M18™ and M12™ Batteries
Charge Sequence	Sequential (First In, First Charged)
Integrated Hang-Holes	Yes
On-Board Indicator Light	Yes
Cell Voltage Monitoring	Yes



Batteries Sold Separately

M12™ LITHIUM-ION Battery Charger

48-59-2401

Specifications:

Compatibility	All M12™ Batteries
Integrated Hang-Holes	Yes
On-Board Indicator Light	Yes
Cell Voltage Monitoring	Yes



M12™ AC/DC Wall and Vehicle Charger

2510-20

Specifications:

Compatibility	All M12™ Batteries
Integrated Hang-Holes	Yes
On-Board Indicator Light	Yes
Cell Voltage Monitoring	Yes



UPGRADE. OUTWORK. OUTLAST.

UP TO **3X** MORE RUN-TIME

UP TO **20%** MORE POWER

OVER **2X** MORE LIFE

REDLITHIUM™ 3.0/XC6.0

M12™ REDLITHIUM™ Compact Battery Pack

48-11-2401

Specifications:

Amp Hours	1.5
Cell Chemistry	LITHIUM-ION



2-Pack Available
48-11-2411



M12™ REDLITHIUM™ XC Extended Capacity Battery Pack

48-11-2402

Specifications:

Amp Hours	3.0
Cell Chemistry	LITHIUM-ION



2-Pack Available
48-11-2412



M12™ REDLITHIUM™ 2.0 Compact Battery Pack

48-11-2420

Specifications:

Amp Hours	2.0
Cell Chemistry	LITHIUM-ION



M12™ REDLITHIUM™ XC4.0 Extended Capacity Battery Pack

48-11-2440

Specifications:

Amp Hours	4.0
Cell Chemistry	LITHIUM-ION



2-Pack Available

M12™ REDLITHIUM™ 3.0 Compact Battery Pack

48-11-2430

Specifications:

Amp Hours	3.0
Cell Chemistry	LITHIUM-ION



M12™ REDLITHIUM™ XC6.0 Extended Capacity Battery Pack

48-11-2460

Specifications:

Amp Hours	6.0
Cell Chemistry	LITHIUM-ION



2-Pack Available

M12™ COMBO KITS

Kit Tool Total	2 - 3 PIECE KITS										4 - 8 PIECE KITS				
	2490-22	2491-22	2492-22	2494-22	2495-22	2497-22	2577-21	2594-22	2597-22	2491-23	2493-23	2493-24	2495-28	2496-24	2499-24
M12™ 1/4" Hex Screwdriver	■									■					
M12 FUEL™ 1/2" Hammer Drill/Driver									■						
M12™ 3/8" Hammer Drill/Driver						■									
M12 FUEL™ 1/2" Drill/Driver								■							
M12™ 3/8" Drill/Driver			■	■	■					■		■	■	■	■
M12™ 3/8" Right Angle Drill/Driver												■			
M12 FUEL™ 1/4" Hex Impact Driver								■	■						
M12™ 1/4" Hex Impact Driver		■		■		■						■	■		
M12™ 3/8" Impact Wrench									■	■					
M12™ HACKZALL® Recip Saw	■	■											■	■	■
M12™ Multi-Tool					■								■		
M12™ 1/4" Ratchet											■				
M12™ Copper Tubing Cutter												■			■
M12™ TRAPSAKE™ 6' Toilet Auger							■								
TRAPSAKE™ 4' Urinal Auger Extension							■								
M12™ M-SPECTOR 360™ Rotating Inspection Scope													■		
M12™ Flashlight									■	■	■	■	■	■	■
M12™ Jobsite Radio			■										■		
Also Includes															
M12™ LITHIUM-ION Battery Charger	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■
M12™ REDLITHIUM™ Compact Battery Pack	2	2	2	2	2	2	1			2	2	2	2	2	2
M12™ REDLITHIUM™ XC Extended Capacity Battery Pack													1		
M12™ REDLITHIUM™ 2.0 Compact Battery Pack								1	1						
M12™ REDLITHIUM™ XC4.0 Extended Capacity Battery Pack								1	1						
Carrying Case								■	■						
Contractor Bag	■	■	■	■	■	■				■	■	■	■	■	■

M18 M12
RAPID CHARGER

- Charges All M18™ and M12™ Batteries
- Charges Batteries Sequentially (First In, First Charged)

CHARGES PACKS UP TO 40% FASTER




REDLITHIUM™ 3.0/XC6.0

- Up to 3X More Run-Time
- Up to 20% More Power
- Over 2X More Life



NUMBER 1 SUBCOMPACT SYSTEM ON THE MARKET





M18

**PERFORMANCE DRIVEN
TRADE FOCUSED
SYSTEM WIDE**

The MILWAUKEE® M18™ cordless system represents the ultimate synergy of professional grade power, extreme performance and superior ergonomics. Powered by REDLITHIUM™ battery technology for unmatched run-time, and coupled with patented technologies, innovative motors and advanced electronics, M18™ changes the game. Focused on improving productivity for professionals in the trades, MILWAUKEE® offers more than 125 performance-driven solutions that are fully compatible with the M18™ family—the fastest growing 18V cordless system on the market.



DRIVEN TO OUTPERFORM.™

For the first time in power tool history, M18 FUEL™ products are delivering game-changing corded performance without the cord. The motors on MILWAUKEE® M18 FUEL™ tools are more powerful and energy efficient—outliving any other brand. To add to the revolutionary technology, M18 FUEL™ possesses the smartest electronics found in any power tool. REDLINK PLUS™ electronics manage an array of power requirements across more than 125 M18™ tools using one common battery. MILWAUKEE® built, the M18™ battery delivers cleaner, more consistent power, lasts longer and delivers more run-time in the harshest jobsite conditions.

M18 FUEL™. Feel the Difference.

M18 FUEL™

LONGER MOTOR LIFE | **MORE** POWER | **MORE** RUN-TIME

NOW AVAILABLE




REDLITHIUM
HIGH DEMAND 9.0

UP TO **5X** MORE RUN-TIME | UP TO **35%** MORE POWER | RUNS UP TO **60%** COOLER

1 POWERSTATE™ BRUSHLESS MOTOR

This best-in-class brushless motor works harder and lives longer than all leading competitors.

- MILWAUKEE® Designed and Built Brushless Motor
- Outperforms All Leading Competitors
- Longer Motor Life




5
YEAR WARRANTY



2 REDLINK PLUS™ INTELLIGENCE

The most advanced system of hardware and software in cordless power tool electronics today.

- Most Advanced Electronic System on the Market for Maximum Performance
- Total System Communication with Overload Protection Increases Tool Life



3 REDLITHIUM™ XC5.0 BATTERY PACK

Compatible with the entire M18™ system, it delivers more run-time, power and recharges than the competition.

- Most Durable Pack on the Market
- Over 2X More Recharges than Leading Competitor
- Fuel Gauge Displays Remaining Charge
- Operates Below -18°C / 0°F



M18
SYSTEM

M18 FUEL
1/2" Hammer Drill/Driver w/ ONE-KEY™ Kit

2706-22 (2706-20 Tool-Only)

Specifications:

Peak Torque	1,200 in-lbs
RPM	0 – 550 / 0 – 2,000
BPM	0 – 32,000
DRIVE CONTROL™	4-Mode (Customizable)
Chuck Type	1/2" Metal Single Sleeve – Ratcheting Lock
Length	7-3/5"
Weight	4.9 lbs

Includes: (2) M18™ REDLITHIUM™ XC5.0 Extended Capacity Battery Packs, Belt Clip, Bit Holder, Side Handle, Multi-Voltage Charger, Carrying Case



M18™ 1/2" Hammer Drill/Driver Kit

2607-22, 2607-22CT (2607-20 Tool-Only)

Specifications:

Peak Torque	525 in-lbs
RPM	0 – 450 / 0 – 1,800
BPM	0 – 28,800
Chuck Type	1/2" Metal Single Sleeve – Ratcheting Lock
Length	7-3/4"
Weight	4.5 lbs

Includes: 2607-22 (2) M18™ REDLITHIUM™ XC Extended Capacity Battery Packs, Multi-Voltage Charger, Carrying Case; 2607-22CT Includes (2) M18™ REDLITHIUM™ Compact Battery Packs



M18 FUEL
1/2" Hammer Drill/Driver Kit

2704-22 (2704-20 Tool-Only)

Specifications:

Peak Torque	1,200 in-lbs
RPM	0 – 550 / 0 – 2,000
BPM	0 – 32,000
Chuck Type	1/2" Metal Single Sleeve – Ratcheting Lock
Length	7-3/4"
Weight	4.9 lbs

Includes: (2) M18™ REDLITHIUM™ XC5.0 Extended Capacity Battery Packs, Belt Clip, Bit Holder, Side Handle, Multi-Voltage Charger, Carrying Case



M18 FUEL
1/2" Drill/Driver w/ ONE-KEY™ Kit

2705-22 (2705-20 Tool-Only)

Specifications:

Peak Torque	1,200 in-lbs
RPM	0 – 550 / 0 – 2,000
DRIVE CONTROL™	4-Mode (Customizable)
Chuck Type	1/2" Metal Single Sleeve – Ratcheting Lock
Length	7-1/5"
Weight	4.8 lbs

Includes: (2) M18™ REDLITHIUM™ XC5.0 Extended Capacity Battery Packs, Belt Clip, Bit Holder, Side Handle, Multi-Voltage Charger, Carrying Case



M18™ 1/2" Compact Brushless Hammer Drill/Driver Kit

2702-22CT (2702-20 Tool-Only)

Specifications:

Peak Torque	1,500 in-lbs
RPM	0 – 450 / 0 – 1,800
BPM	0 – 28,800
Chuck Type	1/2" Metal Single Sleeve – Ratcheting Lock
Length	7-3/8"
Weight	3.8 lbs

Includes: (2) M18™ REDLITHIUM™ 2.0 Compact Battery Packs, Multi-Voltage Charger, Carrying Case



M18 FUEL
1/2" Drill/Driver Kit

2703-22 (2703-20 Tool-Only)

Specifications:

Peak Torque	1,200 in-lbs
RPM	0 – 550 / 0 – 2,000
Chuck type	1/2" Metal Single Sleeve – Ratcheting Lock
Length	7-1/2"
Weight	4.9 lbs

Includes: (2) M18™ REDLITHIUM™ XC5.0 Extended Capacity Battery Packs, Belt Clip, Bit Holder, Side Handle, Multi-Voltage Charger, Carrying Case



M18™ 1/2" Compact Brushless Drill/Driver Kit

2701-22CT (2701-20 Tool-Only)

Specifications:

Peak Torque	500 in-lbs
RPM	0 – 450 / 0 – 1,800
Chuck Type	1/2" Metal Single Sleeve – Ratcheting Lock
Length	6-7/8"
Weight	3.7 lbs

Includes: (2) M18™ REDLITHIUM™ 2.0 Compact Battery Packs, Multi-Voltage Charger, Carrying Case



M18™ 3/8" Right Angle Drill/Driver Kit

2615-21, 2615-21CT (2615-20 Tool-Only)

Specifications:

Peak Torque	125 in-lbs
RPM	0 – 1,500
Clutch Settings	11 Settings plus Drill Mode
Chuck Type	3/8" Single Sleeve
Head Profile	3-3/4"
Weight	4.3 lbs

Includes: 2615-21 (1) M18™ REDLITHIUM™ XC Extended Capacity Battery Pack, Multi-Voltage Charger, Carrying Case; 2615-21CT Includes (1) M18™ REDLITHIUM™ Compact Battery Pack



M18 FUEL
Drywall Screw Gun Kit

2866-22, 2866-22CT (2866-20 Tool-Only)

Specifications:

RPM	0 – 4,500
Belt Clip	Yes
Auto Start Mode	Yes
Length	9"
Weight	4.1 lbs

Includes: 2866-22 (2) M18™ REDLITHIUM™ XC5.0 Extended Capacity Battery Packs, Belt Clip, PR2 Bit, Multi-Voltage Charger, Contractor Bag; 2866-22CT Includes (2) M18™ REDLITHIUM™ 2.0 Compact Battery Packs



Related Accessory:
49-20-0001 MILWAUKEE® Collated Magazine
Screw Capacity: Up to 2"
Compatible with all major screw brands



M18 FUEL HOLE HAWG® Right Angle Drill Kit w/ QUIK-LOK™

2708-22HD, 2708-22 (2708-20 Tool-Only)

Specifications:

RPM	0 – 1,200
Chuck Type	7/16" Hex QUIK-LOK™
Capacity	For Augers up to 1-1/4"; Self-Feed Bits up to 2"
Length	17"
Weight	9.3 lbs

Includes: 2708-22HD (2) M18™ REDLITHIUM™ HIGH DEMAND™ 9.0 Battery Packs, Rapid Charger, Carrying Case; 2708-22 Includes (2) M18™ REDLITHIUM™ XC5.0 Extended Capacity Battery Packs, Multi-Voltage Charger



M18 FUEL HOLE HAWG® 1/2" Right Angle Drill Kit

2707-22HD, 2707-22 (2707-20 Tool-Only)

Specifications:

RPM	0 – 1,200
Chuck Type	1/2" Metal Keyed
Capacity	For Augers up to 1-1/4"; Self-Feed Bits up to 2"
Length	17"
Weight	9.8 lbs

Includes: 2707-22HD (2) M18™ REDLITHIUM™ HIGH DEMAND™ 9.0 Battery Packs, Chuck Key, Rapid Charger, Carrying Case; 2707-22 Includes (2) M18™ REDLITHIUM™ XC5.0 Extended Capacity Battery Packs, Multi-Voltage Charger



M18 FUEL SUPER HAWG™ Right Angle Drill Kit w/ QUIK-LOK™

2711-22HD, 2711-22 (2711-20 Tool-Only)

Specifications:

RPM	0 – 350 / 0 – 950
Chuck Type	7/16" Hex QUIK-LOK™
Capacity	For Self-Feed Bits up to 4-5/8"; Hole Saws up to 6"
Mechanical Clutch	Yes
Length	22"
Weight	14.8 lbs

Includes: 2711-22HD (2) M18™ REDLITHIUM™ HIGH DEMAND™ 9.0 Battery Packs, Side Handle, Rapid Charger, Contractor Bag; 2711-22 Includes (2) M18™ REDLITHIUM™ XC5.0 Extended Capacity Battery Packs



M18 FUEL SUPER HAWG™ 1/2" Right Angle Drill Kit

2709-22HD, 2709-22 (2709-20 Tool-Only)

Specifications:

RPM	0 – 350 / 0 – 950
Chuck Type	1/2" Metal Keyed
Capacity	For Self-Feed Bits up to 4-5/8"; Hole Saws up to 6"
Mechanical Clutch	Yes
Length	22"
Weight	14.9 lbs

Includes: 2709-22HD (2) M18™ REDLITHIUM™ HIGH DEMAND™ 9.0 Battery Packs, Chuck Key, Side Handle, Rapid Charger, Contractor Bag; 2709-22 Includes (2) M18™ REDLITHIUM™ XC5.0 Extended Capacity Battery Packs



M18 FUEL 1-1/2" Magnetic Drill Kit

2787-22HD

Specifications:

Capacity	1-1/2" Annular Cutter; 1/2" Twist Bit
RPM	400 / 690
Magnet	Operates Without Electricity
Dimensions (L x W x H)	13-3/4" x 7-1/2" x 15-1/2"
Weight	30.4 lbs

Includes: (2) M18™ REDLITHIUM™ HIGH DEMAND™ 9.0 Battery Packs, Magnetic Lubrication Tank, 3/4" Weldon to 1/2" Chuck Adapter, Chuck Key, (2) 1" Retracting Pilot Pins, Safety Strap, Rapid Charger, Carrying Case



M18 FUEL 1-1/2" Lineman Magnetic Drill Kit

2788-22HD

Specifications:

Capacity	1-1/2" Annular Cutter; 1/2" Twist Bit
RPM	400 / 690
Magnet	Operates Without Electricity
Dimensions (L x W x H)	13-3/4" x 7-1/2" x 15-1/2"
Weight	30.4 lbs

Includes: (2) M18™ REDLITHIUM™ HIGH DEMAND™ 9.0 Battery Packs, Magnetic Lubrication Tank, 3/4" Weldon to 1/2" Chuck Adapter, Chuck Key, (2) 1" Retracting Pilot Pins, Safety Strap, AC/DC Wall and Vehicle Charger, Carrying Case



M18 FUEL 1-9/16" SDS Max Rotary Hammer Kit

2717-22HD (2717-20 Tool-Only)

Specifications:

RPM	0 – 440
BPM	0 – 3,000
Impact Energy	5.0 ft-lbs
2-Mode Operation	Rotary Hammer and Hammer Only
Weight	13.75 lbs

Includes: (2) M18™ REDLITHIUM™ HIGH DEMAND™ 9.0 Battery Packs, Side Handle, Depth Rod, Rapid Charger, Carrying Case

Related Accessory:

2306-22 M12™ HAMMERVAC™ Universal Dust Extractor



M18 FUEL 1-1/8" SDS Plus Rotary Hammer Kit

2715-22HD, 2715-22, 2715-22DE (2715-20 Tool-Only)

Specifications:

RPM	0 – 1,350
BPM	0 – 5,000
Impact Energy	3.3 ft-lbs
3-Mode Operation	Rotary Hammer, Hammer Only and Rotation Only
Weight	10.1 lbs

Includes: 2715-22HD (2) M18™ REDLITHIUM™ HIGH DEMAND™ 9.0 Battery Packs, Slide Handle, Depth Rod, Rapid Charger, Carrying Case; 2715-22 Includes (2) M18™ REDLITHIUM™ XC5.0 Extended Capacity Battery Packs, Multi-Voltage Charger; 2715-22DE Includes (2) M18™ REDLITHIUM™ XC5.0 Extended Capacity Battery Packs, HAMMERVAC™ Dedicated Dust Extractor, HEPA Filter, Replacement Nozzle, Multi-Voltage Charger



HAMMERVAC™ Dedicated Dust Extractor

2715-DE

Specifications:

Compatibility	For use with 2715-20
In-Line Dedicated Design	Engineered to Fit in the Most Confined Workspaces
Adjustable Depth Stop and Ruler	Easily and Precisely Adjust for Accurate Hole Depths
Replaceable Certified HEPA Filter	Filters 99.97% of Debris 0.3 Microns and Above
Max Bit Size	5/8"

Includes: Replacement Nozzle and HEPA Filter



M18 FUEL 1" SDS Plus Rotary Hammer Kit

2712-22HD, 2712-22, 2712-22DE (2712-20 Tool-Only)

Specifications:

RPM	0 – 1,400
BPM	0 – 4,900
Impact Energy	1.7 ft-lbs
3-Mode Operation	Rotary Hammer, Hammer Only and Rotation Only
Weight	9.4 lbs

Includes: 2712-22HD (2) M18™ REDLITHIUM™ HIGH DEMAND™ 9.0 Battery Packs, Slide Handle, Depth Rod, Rapid Charger, Carrying Case; 2712-22 Includes (2) M18™ REDLITHIUM™ XC5.0 Extended Capacity Battery Packs, Multi-Voltage Charger; 2712-22DE Includes (2) M18™ REDLITHIUM™ XC5.0 Extended Capacity Battery Packs, HAMMERVAC™ Dedicated Dust Extractor, HEPA Filter, Replacement Nozzle, Multi-Voltage Charger



HAMMERVAC™ Dedicated Dust Extractor

2712-DE

Specifications:

Compatibility	For use with 2712-20
In-Line Dedicated Design	Engineered to Fit in the Most Confined Workspaces
Adjustable Depth Stop and Ruler	Easily and Precisely Adjust for Accurate Hole Depths
Replaceable Certified HEPA Filter	Filters 99.97% of Debris 0.3 Microns and Above
Max Bit Size	5/8"

Includes: Replacement Nozzle and HEPA Filter



M18 FUEL 1" SDS Plus D-Handle Rotary Hammer Kit

2713-22HD, 2713-22 (2713-20 Tool-Only)

Specifications:

Capacity	1"
Impact Energy	2.15 ft-lbs
RPM	0 – 1,500
BPM	0 – 4,400
Length	16-1/2"
Weight	8.5 lbs

Includes: 2713-22HD (2) M18™ REDLITHIUM™ HIGH DEMAND™ 9.0 Battery Packs, Slide Handle, Depth Rod, Rapid Charger, Carrying Case; 2713-22 Includes (2) M18™ REDLITHIUM™ XC5.0 Extended Capacity Battery Packs, Multi-Voltage Charger



M18™ 7/8" SDS Plus Rotary Hammer Kit

2605-22 (2605-20 Tool-Only)

Specifications:

RPM	0 – 1,400
BPM	0 – 4,800
Impact Energy	1.4 ft-lbs
3-Mode Operation	Hammer Only, Rotary Hammer and Rotation Only
Weight	7.2 lbs

Includes: (2) M18™ REDLITHIUM™ XC Extended Capacity Battery Packs, Side Handle, Depth Rod, Multi-Voltage Charger, Carrying Case

Related Accessory:

2306-22 M12™ HAMMERVAC™ Universal Dust Extractor



M18™ 5/8" SDS Plus Rotary Hammer Kit

2612-22, 2612-21 (2612-20 Tool-Only)

Specifications:

RPM	0 – 1,300
BPM	0 – 7,000
Impact Energy	1.0 ft-lbs
2-Mode Operation	Rotary Hammer and Rotation Only
Weight	5.5 lbs

Includes: 2612-22 (2) M18™ REDLITHIUM™ XC Extended Capacity Battery Packs, Side Handle, Depth Rod, Multi-Voltage Charger, Carrying Case; 2612-21 Includes (1) M18™ REDLITHIUM™ XC Extended Capacity Battery Pack

Related Accessory:

2306-22 M12™ HAMMERVAC™ Universal Dust Extractor



M18 FUEL
1/4" Hex Impact Driver w/ ONE-KEY™ Kit

2757-22, 2757-22CT (2757-20 Tool-Only)

Specifications:

Fastening Torque	1,800 in-lbs
IPM	0 – 3,700
RPM	0 – 3,000
DRIVE CONTROL™	4-Mode (Customizable)
Chuck Type	1/4" Hex
Length	5-1/4"
Weight	4.0 lbs

Includes: 2757-22 (2) M18™ REDLITHIUM™ XC5.0 Extended Capacity Battery Packs, Belt Clip, Bit Holder, Multi-Voltage Charger, Carrying Case; 2757-22CT Includes (2) M18™ REDLITHIUM™ 2.0 Compact Battery Packs



M18 FUEL
1/4" Hex Impact Driver Kit

2753-22, 2753-22CT (2753-20 Tool-Only)

Specifications:

Fastening Torque	1,800 in-lbs
IPM	0 – 3,700
RPM	0 – 3,000
DRIVE CONTROL™	4-Mode
Chuck Type	1/4" Hex
Length	5-1/4"
Weight	3.9 lbs

Includes: 2753-22 (2) M18™ REDLITHIUM™ XC5.0 Extended Capacity Battery Packs, Belt Clip, Bit Holder, Multi-Voltage Charger, Carrying Case; 2753-22CT Includes (2) M18™ REDLITHIUM™ 2.0 Compact Battery Packs



M18™ 1/4" Hex Brushless Impact Driver Kit

2750-22CT (2750-20 Tool-Only)

Specifications:

Fastening Torque	1,500 in-lbs
IPM	0 – 3,600
RPM	0 – 2,900
Chuck Type	1/4" Hex
Length	5-3/8"
Weight	3.1 lbs

Includes: (2) M18™ REDLITHIUM™ 2.0 Compact Capacity Battery Packs, Belt Clip, Multi-Voltage Charger, Carrying Case



M18 FUEL
SURGE™ 1/4" Hex Hydraulic Driver Kit

2760-22, 2760-22CT (2760-20 Tool-Only)

Specifications:

Sustained Fastening Torque	450 in-lbs
IPM	0 – 4,000
RPM	0 – 3,000
DRIVE CONTROL™	4-Mode
Length	5"
Weight	3.9 lbs

Includes: 2760-22 (2) M18™ REDLITHIUM™ XC5.0 Extended Capacity Battery Packs, Belt Clip, Bit Holder, Multi-Voltage Charger, Carrying Case; 2760-22CT Includes (2) M18™ REDLITHIUM™ 2.0 Battery Packs



M18™ 1/4" Hex Compact Impact Driver Kit

2656-22CT (2656-20 Tool-Only)

Specifications:

Fastening Torque	1,500 in-lbs
IPM	0 – 3,450
RPM	0 – 2,750
Chuck Type	1/4" Hex Quick Change
Length	5-1/2"
Weight	3.8 lbs

Includes: 2657-22 (2) M18™ REDLITHIUM™ Compact Battery Packs, Belt Clip, Multi-Voltage Charger, Carrying Case



M18™ 1/4" 2-Speed Impact Driver Kit

2657-22, 2657-22CT (2657-20 Tool-Only)

Specifications:

Fastening Torque	1,500 in-lbs
IPM	0 – 3,450
RPM	0 – 2,750
Chuck Type	1/4" Hex Quick Change
Length	5-1/2"
Weight	3.8 lbs

Includes: 2657-22 (2) M18™ REDLITHIUM™ XC Extended Capacity Battery Packs, Belt Clip, Multi-Voltage Charger, Carrying Case; 2657-22CT Includes (2) M18™ REDLITHIUM™ Compact Battery Packs



M18 FUEL
3/8" Impact Wrench w/ Friction Ring w/ ONE-KEY™ Kit

2758-22, 2758-22CT (2758-20 Tool-Only)

Specifications:

Fastening Torque	210 ft-lbs
IPM	0 – 3,200
RPM	0 – 2,500
DRIVE CONTROL™	4-Mode (Customizable)
Chuck Type	3/8" Friction Ring
Length	5-9/10"
Weight	4.2 lbs

Includes: 2758-22 (2) M18™ REDLITHIUM™ XC5.0 Extended Capacity Battery Packs, Belt Clip, Bit Holder, Multi-Voltage Charger, Carrying Case; 2758-22CT Includes (2) M18™ REDLITHIUM™ 2.0 Compact Battery Packs



M18 FUEL
3/8" Compact Impact Wrench w/ Friction Ring Kit

2754-22, 2754-22CT (2754-20 Tool-Only)

Specifications:

Fastening Torque	210 ft-lbs
IPM	0 – 3,200
RPM	0 – 2,500
DRIVE CONTROL™	4-Mode
Chuck Type	3/8" Friction Ring
Length	5-9/10"
Weight	4.2 lbs

Includes: 2754-22 (2) M18™ REDLITHIUM™ XC5.0 Extended Capacity Battery Packs, Belt Clip, Bit Holder, Multi-Voltage Charger, Carrying Case; 2754-22CT Includes (2) M18™ REDLITHIUM™ 2.0 Compact Battery Packs



M18™ 3/8" Compact Impact Wrench Kit

2658-22, 2658-22CT (2658-20 Tool-Only)

Specifications:

Fastening Torque	167 ft-lbs
IPM	0 – 3,350
RPM	0 – 2,450
Anvil	3/8" Friction Ring
Length	6"
Weight	4.1 lbs

Includes: 2658-22 (2) M18™ REDLITHIUM™ XC Extended Capacity Battery Packs, Belt Clip, Multi-Voltage Charger, Carrying Case; 2658-22CT Includes (2) M18™ REDLITHIUM™ Compact Battery Packs



M18 FUEL
1/2" Compact Impact Wrench w/ Pin Detent w/ ONE-KEY™ Kit

2759-22, 2759B-22 (2759-20, 2759B-20 Tool-Only)

Specifications:

Fastening Torque	220 ft-lbs
IPM	0 – 3,200
RPM	0 – 2,500
DRIVE CONTROL™	4-Mode (Customizable)
Chuck Type	1/2" Pin Detent
Length	6-1/10"
Weight	4.2 lbs

Includes: 2759-22 (2) M18™ REDLITHIUM™ XC5.0 Extended Capacity Battery Packs, Belt Clip, Bit Holder, Multi-Voltage Charger, Carrying Case; 2759B-22 1/2" Compact Impact Wrench w/ Friction Ring w/ ONE-KEY™ Kit



M18 FUEL
1/2" Compact Impact Wrench w/ Pin Detent Kit

2755-22, 2755B-22 (2755-20, 2755B-20 Tool-Only)

Specifications:

Fastening Torque	220 ft-lbs
IPM	0 – 3,200
RPM	0 – 2,500
DRIVE CONTROL™	4-Mode
Chuck Type	1/2" Pin Detent
Length	6-1/10"
Weight	4.2 lbs

Includes: 2755-22 (2) M18™ REDLITHIUM™ XC5.0 Extended Capacity Battery Packs, Belt Clip, Bit Holder, Multi-Voltage Charger, Carrying Case; 2755B-22 1/2" Compact Impact Wrench w/ Friction Ring Kit



M18™ 1/2" Compact Impact Wrench Kit

2659-22 (2659-20 Tool-Only)

Specifications:

Fastening Torque	183 ft-lbs
IPM	0 – 3,350
RPM	0 – 2,450
Anvil	1/2" Pin Detent
Length	6"
Weight	4.1 lbs

Includes: (2) M18™ REDLITHIUM™ XC Extended Capacity Battery Packs, Belt Clip, Multi-Voltage Charger, Carrying Case



M18™ Right Angle Impact Wrench Kit

2668-22, 2668-21CT (2668-20 Tool-Only)

Specifications:

Fastening Torque (2-Mode)	30 / 60 ft-lbs
IPM	0 – 2,400 / 0 – 3,400
RPM	0 – 1,500 / 0 – 2,250
Chuck Type	3/8"
Length	14-1/4"
Weight	3.9 lbs

Includes: 2668-22 (2) M18™ REDLITHIUM™ XC Extended Capacity Battery Packs, Belt Clip, Multi-Voltage Charger, Carrying Case; 2668-21CT Includes (1) M18™ REDLITHIUM™ Compact Battery Pack



M18™ Right Angle Impact Driver Kit

2667-22, 2667-21CT (2667-20 Tool-Only)

Specifications:

Fastening Torque (2-Mode)	350 / 675 in-lbs
IPM	0 – 2,400 / 0 – 3,400
RPM	0 – 1,500 / 0 – 2,250
Chuck Type	1/4" Hex
Length	14-1/8"
Weight	3.9 lbs

Includes: 2667-22 (2) M18™ REDLITHIUM™ XC Extended Capacity Battery Packs, Belt Clip, Multi-Voltage Charger, Carrying Case; 2667-21CT Includes (1) M18™ REDLITHIUM™ Compact Battery Pack



M18 FUEL™ 1/2" Mid-Torque Impact Wrench w/ Pin Detent Kit

2860-22 (2860-20 Tool-Only)

Specifications:

Fastening Torque	450 ft-lbs
Nut Busting Torque	600 ft-lbs
IPM	0 – 3,000
RPM	0 – 2,400
Chuck Type	1/2" Pin Detent
Length	6-7/10"
Weight	5.3 lbs

Includes: (2) M18™ REDLITHIUM™ XC5.0 Battery Packs, Belt Clip, Multi-Voltage Charger, Carrying Case



M18 FUEL™ 1/2" Mid-Torque Impact Wrench w/ Friction Ring Kit

2861-22 (2861-20 Tool-Only)

Specifications:

Fastening Torque	450 ft-lbs
Nut Busting Torque	600 ft-lbs
IPM	0 – 3,000
RPM	0 – 2,400
Chuck Type	1/2" Friction Ring
Length	6-7/10"
Weight	5.3 lbs

Includes: (2) M18™ REDLITHIUM™ XC5.0 Battery Packs, Belt Clip, Multi-Voltage Charger, Carrying Case



M18 FUEL™ 1/2" High Torque Impact Wrench w/ Pin Detent Kit

2762-22 (2762-20 Tool-Only)

Specifications:

Max Fastening Torque (2-Mode)	350 / 600 ft-lbs
Nut-Busting Torque	900 ft-lbs
IPM	0 – 2,300
RPM (2-Mode)	0 – 1,200 / 0 – 1,700
Anvil	1/2" Pin Detent
Length	8-3/4"
Weight	7.3 lbs

Includes: (2) M18™ REDLITHIUM™ XC5.0 Extended Capacity Battery Packs, Multi-Voltage Charger, Carrying Case



M18™ 1/2" High Torque Impact Wrench w/ Pin Detent Kit

2662-22 (2662-20 Tool-Only)

Specifications:

Fastening Torque	450 ft-lbs
Breakaway Torque	640 ft-lbs
IPM	0 – 2,200
RPM	0 – 1,900
Anvil	1/2" Pin Detent
Length	8-7/8"
Weight	6.7 lbs

Includes: (2) M18™ REDLITHIUM™ XC Extended Capacity Battery Packs, Multi-Voltage Charger, Carrying Case



M18 FUEL™ 1/2" High Torque Impact Wrench w/ Friction Ring Kit

2763-22 (2763-20 Tool-Only)

Specifications:

Max Fastening Torque (2-Mode)	100 / 700 ft-lbs
Nut-Busting Torque	1,100 ft-lbs
IPM	0 – 2,300
RPM (2-Mode)	0 – 350 / 0 – 1,700
Anvil	1/2" Friction Ring
Length	9"
Weight	7.5 lbs

Includes: (2) M18™ REDLITHIUM™ XC5.0 Extended Capacity Battery Packs, Multi-Voltage Charger, Carrying Case



M18™ 1/2" High Torque Impact Wrench w/ Friction Ring Kit

2663-22 (2663-20 Tool-Only)

Specifications:

Fastening Torque	450 ft-lbs
Breakaway Torque	640 ft-lbs
IPM	0 – 2,200
RPM	0 – 1,900
Anvil	1/2" Friction Ring
Length	8-7/8"
Weight	6.7 lbs

Includes: (2) M18™ REDLITHIUM™ XC Extended Capacity Battery Packs, Multi-Voltage Charger, Carrying Case



M18 FUEL™ 3/4" High Torque Impact Wrench w/ Friction Ring Kit

2764-22 (2764-20 Tool-Only)

Specifications:

Max Fastening Torque (2-Mode)	375 / 750 ft-lbs
Nut-Busting Torque	1,200 ft-lbs
IPM	0 – 2,300
RPM (2-Mode)	0 – 1,200 / 0 – 1,700
Anvil	3/4" Friction Ring
Length	9"
Weight	7.5 lbs

Includes: (2) M18™ REDLITHIUM™ XC5.0 Extended Capacity Battery Packs, Multi-Voltage Charger, Carrying Case



M18™ 3/4" High Torque Impact Wrench w/ Friction Ring Kit

2664-22 (2664-20 Tool-Only)

Specifications:

Fastening Torque	525 ft-lbs
Breakaway Torque	700 ft-lbs
IPM	0 – 2,200
RPM	0 – 1,900
Anvil	3/4" Friction Ring
Length	9"
Weight	6.8 lbs

Includes: (2) M18™ REDLITHIUM™ XC Extended Capacity Battery Packs, Multi-Voltage Charger, Carrying Case



M18 FUEL
7/16" Hex Utility High Torque Impact Kit

2765-22 (2765-20 Tool-Only)

Specifications:

Max Fastening Torque (2-Mode)	300 / 500 ft-lbs
IPM	0 – 2,300
RPM (2-Mode)	0 – 1,200 / 0 – 1,700
Anvil	7/16" Hex
Length	8-3/4"
Weight	7.1 lbs

Includes: (2) M18™ REDLITHIUM™ XC5.0 Extended Capacity Battery Packs, Hanger Ring, Banger Bracket, AC/DC Wall and Vehicle Charger, Contractor Bag



M18™ 7/16" Hex Utility High Torque Impact Kit

2665-22 (2665-20 Tool-Only)

Specifications:

Fastening Torque	350 ft-lbs
IPM	0 – 2,200
RPM	0 – 1,900
Anvil	7/16" Hex
Length	9-1/2"
Weight	7.0 lbs

Includes: (2) M18™ REDLITHIUM™ XC Extended Capacity Battery Packs, Multi-Voltage Charger, Contractor Bag



M18 FUEL
SAWZALL® Recip Saw w/ ONE-KEY™ Kit

2721-22HD, 2721-22 (2721-20 Tool-Only)

Specifications:

SPM	0 – 3,000
Stroke Length	1-1/8"
Blade Clamp	Lever-Action QUIK-LOK™ (Accepts all SAWZALL® Blades)
Cut Control	4-Mode (Customizable)
Anti-Vibration	Yes
Weight	8.9 lbs

Includes: 2721-22HD (2) M18™ REDLITHIUM™ HIGH DEMAND™ 9.0 Battery Packs, Blade, Rapid Charger, Carrying Case; 2721-22 Includes (2) M18™ REDLITHIUM™ XC5.0 Extended Capacity Battery Packs, Multi-Voltage Charger



M18 FUEL
SAWZALL® Recip Saw Kit

2720-22HD, 2720-22, 2720-21 (2720-20 Tool-Only)

Specifications:

SPM	0 – 3,000
Stroke Length	1-1/8"
Blade Clamp	Lever-Action QUIK-LOK™ (Accepts all SAWZALL® Blades)
Anti-Vibration	Yes
Weight	9.8 lbs

Includes: 2720-22HD (2) M18™ REDLITHIUM™ HIGH DEMAND™ 9.0 Battery Packs, Blade, Rapid Charger, Carrying Case; 2720-22 Includes (2) M18™ REDLITHIUM™ XC5.0 Extended Capacity Battery Packs, Multi-Voltage Charger; 2720-21 Includes (1) M18™ REDLITHIUM™ XC5.0 Extended Capacity Battery Pack, Multi-Voltage Charger



M18™ SAWZALL® Recip Saw Kit

2621-22, 2621-21 (2621-20 Tool-Only)

Specifications:

SPM	0 – 3,000
Stroke Length	1-1/8"
Blade Clamp	Lever-Action QUIK-LOK™ (Accepts all SAWZALL® Blades)
Anti-Vibration	Yes
Weight	7.9 lbs

Includes: 2621-22 (2) M18™ REDLITHIUM™ XC Extended Capacity Battery Packs, Blade, Multi-Voltage Charger, Carrying Case; 2621-21 Includes (1) M18™ REDLITHIUM™ XC Extended Capacity Battery Pack



M18™ HACKZALL® One-Handed Recip Saw Kit

2625-21, 2625-21CT (2625-20 Tool-Only)

Specifications:

SPM	0 – 3,000
Stroke Length	3/4"
Blade Clamp	QUIK-LOK™ (Accepts all SAWZALL® Blades)
Anti-Vibration	Yes
Weight	5.6 lbs

Includes: 2625-21 (1) M18™ REDLITHIUM™ XC Extended Capacity Battery Pack, Blade, Multi-Voltage Charger, Contractor Bag; 2625-21CT Includes (1) M18™ REDLITHIUM™ Compact Battery Pack



M18 FUEL
7-1/4" Circular Saw Kit

2731-22HD, 2731-22, 2731-21 (2731-20 Tool-Only)

Specifications:

RPM	5,000
Bevel Capacity	50°
Cut Capacity	2-1/2" at 90°; 1-7/8" at 45°
Arbor	5/8"
Blade Guards	Magnesium
Weight	9.9 lbs

Includes: 2731-22HD (2) M18™ REDLITHIUM™ HIGH DEMAND™ 9.0 Battery Packs, Circular Saw Blade, Wrench, Rapid Charger, Contractor Bag; 2731-22 Includes (2) M18™ REDLITHIUM™ XC5.0 Extended Capacity Battery Packs, Multi-Voltage Charger; 2731-21 Includes (1) M18™ REDLITHIUM™ XC5.0 Extended Capacity Battery Pack, Multi-Voltage Charger



M18™ 3-1/4" Planer Kit

2623-21 (2623-20 Tool-Only)

Specifications:

RPM	14,000
Planing Width	3-1/4"
Max Planing Depth	5/64"
Rabbit Depth	27/64"
Length	12-2/5"
Weight	7.8 lbs

Includes: (1) M18™ REDLITHIUM™ XC Extended Capacity Battery Pack, Bevel Edge Guide, (2) Double Edged Carbide Blades, Multi-Voltage Charger, Contractor Bag



M18 FUEL
6-1/2" Circular Saw Kit

2730-22, 2730-21 (2730-20 Tool-Only)

Specifications:

RPM	5,000
Bevel Capacity	50°
Cut Capacity	2-3/16" at 90°; 1-5/8" at 45°
Arbor	5/8"
Blade Guards	Magnesium
Weight	8.0 lbs

Includes: 2730-22 (2) M18™ REDLITHIUM™ XC5.0 Extended Capacity Battery Packs, Circular Saw Blade, Wrench, Multi-Voltage Charger, Contractor Bag; 2730-21 Includes (1) M18™ REDLITHIUM™ XC5.0 Extended Capacity Battery Pack



M18™ 6-1/2" Circular Saw Kit

2630-22 (2630-20 Tool-Only)

Specifications:

RPM	3,500
Bevel Capacity	50°
Cut Capacity	2-1/8" at 90°; 1-9/16" at 45°
Arbor	5/8"
Blade Guards	Magnesium
Weight	8.5 lbs

Includes: (2) M18™ REDLITHIUM™ XC Extended Capacity Battery Packs, Circular Saw Blade, Rip Fence, Wrench, Multi-Voltage Charger, Contractor Bag



M18™ Jig Saw Kit

2645-22 (2645-20 Tool-Only)

Specifications:

SPM	0 – 2,700
Stroke Length	1"
Bevel Capacity	45° (Positive Locks at 0°, 15°, 30° and 45°)
Blade Clamp	QUIK-LOK™ T-Shank
Orbital Settings	5
Weight	7.7 lbs

Includes: (2) M18™ REDLITHIUM™ XC Extended Capacity Battery Packs, Jig Saw Blade, Non-Marring Shoe, Multi-Voltage Charger, Carrying Case



M18™ Multi-Tool Kit

2626-22 (2626-20 Tool-Only)

Specifications:

Speed Settings	12
OPM	11,000 – 18,000
Universal Adapter	Yes
Tool Free Accessory Change	Yes
Length	14"
Weight	4.2 lbs

Includes: (2) M18™ REDLITHIUM™ XC Extended Capacity Battery Packs, Wood Cutting Blade, Sanding Pad, (5) Assorted Sanding Sheets, Multi-Voltage Charger, Contractor Bag



M18™ Band Saw Kit

2629-22 (2629-20 Tool-Only)

Specifications:

SFPM	480
Cut Capacity	3-1/4" x 3-1/4"
Shoe	Tool Free
LED Light	Yes
Weight	10.2 lbs

Includes: (2) M18™ REDLITHIUM™ XC Extended Capacity Battery Packs, Blade, Multi-Voltage Charger, Carrying Case



M18 FUEL

10" Dual Bevel Sliding Compound Miter Saw Kit

2734-21HD (2734-20 Tool-Only)

Specifications:

Blade Size	10"
No Load RPM	4,000
Max Bevel Angle	48° / 48°
Max Miter Angle	50° / 60°
Max Vertical Capacity	5-3/4"
Max Horizontal Capacity	2x12
Weight	47.0 lbs

Includes: (1) M18™ REDLITHIUM™ HIGH DEMAND™ 9.0 Battery Pack, Blade Wrench, Carbide Tipped Blade, Clamp, Dust Bag, Rapid Charger



M18™ Cut Out Tool Kit

2627-22, 2627-22CT (2627-20 Tool-Only)

Specifications:

RPM	28,000
Tool Free Adjustment	Yes
LED Light	Yes
Belt Clip	Yes
Length	8-9/10"
Weight	1.9 lbs

Includes: 2627-22 (2) M18™ REDLITHIUM™ Extended Capacity XC Battery Packs, Belt Clip, (2) 1/8" Drywall Bits, 1/8" Collet, 1/4" Collet, Wrench, Multi-Voltage Charger, Contractor Bag; 2627-22CT Includes (2) M18™ REDLITHIUM™ Compact Battery Packs



M18 FUEL

16 Gauge Angled Finish Nailer Kit

2742-21CT (2742-20 Tool-Only)

Specifications:

Nail Diameter	16 gauge
Nail Size	1-1/4" – 2-1/2"
Nail Collation Angle	20°
Magazine Size	110 Nails
Max Fire Rate	3 Nails per Second
Magazine Loading	Bottom Load
Length	11-9/10"
Weight	7.2 lbs

Includes: (1) M18™ REDLITHIUM™ 2.0 Compact Battery Pack, Multi-Voltage Charger, Contractor Bag



M18 FUEL

Metal Cutting Circular Saw Kit

2782-22 (2782-20 Tool-Only)

Specifications:

RPM	3,900
Blade Size	5-3/8" – 5-7/8"
Arbor Size	20 mm
Hang Hook	Yes
Length	4-7/10"
Weight	6.5 lbs

Includes: (2) M18™ REDLITHIUM™ XC5.0 Extended Capacity Battery Packs, 30T Blade, Multi-Voltage Charger, Contractor Bag



M18 FUEL

18 Gauge Brad Nailer Kit

2740-21CT (2740-20 Tool-Only)

Specifications:

Nail Diameter	18 gauge
Nail Size	5/8" – 2-1/8"
Nail Collation Angle	0°
Magazine Size	110 Nails
Max Fire Rate	3 Nails per Second
Magazine Loading	Side Load
Length	11-2/5"
Weight	6.1 lbs

Includes: (1) M18™ REDLITHIUM™ 2.0 Compact Battery Pack, Multi-Voltage Charger, Contractor Bag



M18 FUEL

15 Gauge Finish Nailer Kit

2743-21CT (2743-20 Tool-Only)

Specifications:

Nail Diameter	15 gauge
Nail Size	1-1/4" – 2-1/2"
Nail Collation Angle	34°
Magazine Size	110 Nails
Max Fire Rate	3 Nails per Second
Magazine Loading	Bottom Load
Length	11-9/10"
Weight	7.2 lbs

Includes: (1) M18™ REDLITHIUM™ 2.0 Compact Battery Pack, Multi-Voltage Charger, Contractor Bag



M18 FUEL
Deep Cut Band Saw Kit

2729-22HD, 2729-22, 2729-21 (2729-20 Tool-Only)

Specifications:

SFPM	0 – 380
Cut Capacity	5" x 5"
Shoe	Tool Free
LED Light	Yes
Hang Hook	Yes
Weight	15.9 lbs

Includes: 2729-22HD (2) M18™ REDLITHIUM™ HIGH DEMAND™ 9.0 Battery Packs, Blade, Rapid Charger, Carrying Case; 2729-22 Includes (2) M18™ REDLITHIUM™ XC5.0 Extended Capacity Battery Packs, Multi-Voltage Charger; 2729-21 Includes (1) M18™ REDLITHIUM™ XC5.0 Extended Capacity Battery Pack, Multi-Voltage Charger



M18 FUEL

16 Gauge Straight Finish Nailer Kit

2741-21CT (2741-20 Tool-Only)

Specifications:

Nail Diameter	16 gauge
Nail Size	3/4" – 2-1/2"
Nail Collation Angle	0°
Magazine Size	110 Nails
Max Fire Rate	3 Nails per Second
Magazine Loading	Bottom Load
Length	11-9/10"
Weight	7.2 lbs

Includes: (1) M18™ REDLITHIUM™ 2.0 Compact Battery Pack, Multi-Voltage Charger, Contractor Bag



M18 FUEL
7" Variable Speed Polisher Kit

2738-22, 2738-22P (2738-20 Tool-Only)

Specifications:

Capacity	7" Maximum
RPM	0 – 2,200
Variable Speed Dial and Trigger	Yes
Lock-On / Lock-Off	Yes
Length	19-4/5"
Weight	6.4 lbs



Includes: 2738-22 (2) M18™ REDLITHIUM™ XC5.0 Battery Packs, Backing Pad, Screen Cover, Side Handle, Bail Handle with (2) Bolts, Rapid Charger; 2738-22P Includes 7" Wool Cutting Pad, 7" Yellow Foam Polishing Pad, 7" Black Foam Finishing Pad



M18 FUEL
4-1/2" / 5" Grinder Paddle Switch, No-Lock Kit

2780-22HD, 2780-22, 2780-21 (2780-20 Tool-Only)

Specifications:

RPM	8,500
Switch Type	Paddle No-Lock
Power to Grind	Yes
Overload Protection	Yes
Electronic Clutch	Yes
Tool Free Accessory Change and Guard	Yes
Length	15"
Weight	8.2 lbs



Includes: 2780-22HD (2) M18™ REDLITHIUM™ HIGH DEMAND™ 9.0 Battery Packs, Rapid Charger, Carrying Case; 2780-22 Includes (2) M18™ REDLITHIUM™ XC5.0 Extended Capacity Battery Packs, Multi-Voltage Charger; 2780-21 Includes (1) M18™ REDLITHIUM™ XC5.0 Extended Capacity Battery Pack, Multi-Voltage Charger



M18 FUEL
4-1/2" / 5" Grinder Slide Switch, Lock-On Kit

2781-22HD, 2781-22, 2781-21 (2781-20 Tool-Only)

Specifications:

RPM	8,500
Switch Type	Slide with Lock-On
Power to Grind	Yes
Overload Protection	Yes
Electronic Clutch	Yes
Tool Free Accessory Change and Guard	Yes
Length	15"
Weight	8.2 lbs



Includes: 2781-22HD (2) M18™ REDLITHIUM™ HIGH DEMAND™ 9.0 Battery Packs, Rapid Charger, Carrying Case; 2781-22 Includes (2) M18™ REDLITHIUM™ XC5.0 Extended Capacity Battery Packs, Multi-Voltage Charger; 2781-21 Includes (1) M18™ REDLITHIUM™ XC5.0 Extended Capacity Battery Pack, Multi-Voltage Charger



M18 FUEL
4-1/2" / 5" Braking Grinder Kit

2783-22HD, 2783-22 (2783-20 Tool-Only)

Specifications:

RPM	8,500
Switch Type	Paddle No-Lock
Brake	Yes
Clutch	Yes
Overload Protection	Yes
Tool Free Accessory Change and Guard	FIXTEC™ Nut and Tool Free Guard
Length	15-1/4"
Weight	8.2 lbs



Includes: 2783-22HD (2) M18™ REDLITHIUM™ HIGH DEMAND™ 9.0 Battery Packs, FIXTEC™ Nut, Flange Nut, T1 Guard, T27 Guard, Rapid Charger, Carrying Case; 2783-22 Includes (2) M18™ REDLITHIUM™ XC5.0 Extended Capacity Battery Packs, Multi-Voltage Charger

M18 FUEL
1/4" Die Grinder Kit

2784-22 (2784-20 Tool-Only)

Specifications:

Collet Size	1/4"
RPM	20,000
Switch Type	Slide, Lock-On
Length	18"
Weight	4.6 lbs



Includes: (2) M18™ REDLITHIUM™ XC5.0 Extended Capacity Battery Packs, 11/16" Wrench, 1/2" Wrench, Multi-Voltage Charger, Carrying Case



M18™ 4-1/2" Cut-Off / Grinder Kit

2680-22 (2680-20 Tool-Only)

Specifications:

RPM	9,000
Switch	Paddle
Guard Adjustment	Tool Free
Overload Protection	Yes
Weight	5.9 lbs



Includes: (2) M18™ REDLITHIUM™ XC Extended Capacity Battery Packs, Type 1 Guard, Type 27 Guard, Spanner Wrench, Side Handle, Multi-Voltage Charger, Contractor Bag



M18™ 18 Gauge Double Cut Shear Kit

2635-22 (2635-20 Tool-Only)

Specifications:

Head	18 Gauge Double Cut
360° Tool Free Rotating Head	Yes
Variable Speed Trigger	Yes
Length	17-1/4"
Weight	5.6 lbs



Includes: (2) M18™ REDLITHIUM™ XC Extended Capacity Battery Packs, Hex Key, Belt Clip, Multi-Voltage Charger, Contractor Bag

M18™ 14 Gauge Double Cut Shear Kit

2636-22 (2636-20 Tool-Only)

Specifications:

Head	14 Gauge Double Cut
360° Tool Free Rotating Head	Yes
Variable Speed Trigger	Yes
Length	17-1/4"
Weight	6.2 lbs



Includes: (2) M18™ REDLITHIUM™ XC Extended Capacity Battery Packs, Hex Key, Belt Clip, Multi-Voltage Charger, Contractor Bag

M18™ 18 Gauge Single Cut Shear Kit

2637-22 (2637-20 Tool-Only)

Specifications:

Head	18 Gauge Single Cut
360° Tool Free Rotating Head	Yes
Variable Speed Trigger	Yes
Length	18"
Weight	5.8 lbs



Includes: (2) M18™ REDLITHIUM™ XC Extended Capacity Battery Packs, Hex Key, Belt Clip, Multi-Voltage Charger, Contractor Bag

M18™ FORCE LOGIC™ 6T Crimper Kit w/ D3 Grooves and Fixed BG Die

2678-22BG

Specifications:

Balanced Center Grip	Yes
Adaptive Pressure Control System	Yes; PFM™
Reporting and Tool Diagnostics	Built-In; ONE-KEY™ Compatible
Crimp Speed	2.9 Seconds
Head Rotation	350°
Length	14"



Includes: (2) M18™ REDLITHIUM™ 2.0 Compact Battery Packs, 6T Crimping Jaw with Fixed BG Die, Carabiner, AC/DC Wall and Vehicle Charger, Bucket Bag



M18™ FORCE LOGIC™ 6T Crimper Kit w/ D3 Grooves and Fixed O Die

2678-22O

Specifications:

Balanced Center Grip	Yes
Adaptive Pressure Control System	Yes; PFM™
Reporting and Tool Diagnostics	Built-In; ONE-KEY™ Compatible
Crimp Speed	2.9 Seconds
Head Rotation	350°
Length	14"



Includes: (2) M18™ REDLITHIUM™ 2.0 Compact Battery Packs, 6T Crimping Jaw with Fixed O Die, Carabiner, AC/DC Wall and Vehicle Charger, Bucket Bag

M18™ FORCE LOGIC™ 6T Crimper Kit w/ D3 Grooves and Snub Nose

2678-22

Specifications:

Balanced Center Grip	Yes
Adaptive Pressure Control System	Yes; PFM™
Reporting and Tool Diagnostics	Built-In; ONE-KEY™ Compatible
Crimp Speed	2.9 Seconds
Head Rotation	350°
Length	14"



Includes: (2) M18™ REDLITHIUM™ 2.0 Compact Battery Packs, 6T Snub Nose Crimping Jaw, Carabiner, AC/DC Wall and Vehicle Charger, Bucket Bag

M18™ FORCE LOGIC™ 6T Crimper Kit w/ Kearney Grooves

2678-22K

Specifications:

Balanced Center Grip	Yes
Adaptive Pressure Control System	Yes; PFM™
Reporting and Tool Diagnostics	Built-In; ONE-KEY™ Compatible
Crimp Speed	2.9 Seconds
Head Rotation	350°
Length	14"



Includes: (2) M18™ REDLITHIUM™ 2.0 Compact Battery Packs, 6T Kearney Crimping Jaw, Carabiner, AC/DC Wall and Vehicle Charger, Bucket Bag

M18™ FORCE LOGIC™ 6T Crimper Accessories

Compatible with 2678-22BG, 2678-22O, 2678-22, 2678-22K

6T Utility Crimper Jaws

- 49-16-BGD3 6T Fixed BG Crimping Jaw;
- 49-16-0OD3 6T Fixed O Crimping Jaw;
- 49-16-00D3 6T Snub Nose Crimping Jaw;
- 49-16-KEAR 6T Kearney Crimping Jaw

W Style Dies

- 49-16-WBG0 W Style Die: "W-BG";
- 49-16-WO00 W Style Die: "W-O";
- 49-16-WC00 W Style Die: "W-C";
- 49-16-W840 W Style Die: "W-K840";
- 49-16-W161 W Style Die: "W-161";
- 49-16-W162 W Style Die: "W-162";
- 49-16-W163 W Style Die: "W-163";
- 49-16-W165 W Style Die: "W-165";
- 49-16-W166 W Style Die: "W-166";
- 49-16-W243 W Style Die: "W-243";
- 49-16-W247 W Style Die: "W-247";
- 49-16-W249 W Style Die: "W-249";
- 49-16-W164 W Style Die: "W-164";
- 49-16-W237 W Style Die: "W-237";
- 49-16-W239 W Style Die: "W-239"



M18™ FORCE LOGIC™ 600 MCM Crimper Kit

2679-22

Specifications:

UL Classification	Yes (All 7 Manufacturers)
Balanced Center Grip	Yes
Adaptive Pressure Control System	Yes; PFM™
Reporting and Tool Diagnostics	Built-In; ONE-KEY™ Compatible
Crimp Speed	2.9 Seconds
Head Rotation	350°
Length	14"



Includes: (2) M18™ REDLITHIUM™ 2.0 Compact Battery Packs, 600 MCM Commercial U Crimping Jaw, Multi-Voltage Charger, Carrying Case

Related Accessories:

49-16-U000 600 MCM Crimping Jaw

Accessory Kits

- 49-16-KITA #8 AWG – 350 MCM Aluminum U Style Die Kit;
- 49-16-KITC #8 AWG – 600 MCM Copper U Style Die Kit

Copper U Style Dies

- 49-16-U008C #8 Copper 12T U Style Die;
- 49-16-U006C #6 Copper 12T U Style Die;
- 49-16-U004C #4 Copper 12T U Style Die;
- 49-16-U002C #2 Copper 12T U Style Die;
- 49-16-U001C #1 Copper 12T U Style Die;
- 49-16-U01AC 1/0 Copper 12T U Style Die;
- 49-16-U02AC 2/0 Copper 12T U Style Die;
- 49-16-U03AC 3/0 Copper 12T U Style Die;
- 49-16-U04AC 4/0 Copper 12T U Style Die;
- 49-16-U250C 250 MCM Copper 12T U Style Die;
- 49-16-U300C 300 MCM Copper 12T U Style Die;
- 49-16-U350C 350 MCM Copper 12T U Style Die;
- 49-16-U400C 400 MCM Copper 12T U Style Die;
- 49-16-U500C 500 MCM Copper 12T U Style Die;
- 49-16-U600C 600 MCM Copper 12T U Style Die

Aluminum Dual Rated U Style Dies

- 49-16-U008 #8 Aluminum U Style Die;
- 49-16-U006 #6 Aluminum U Style Die;
- 49-16-U004 #4 Aluminum U Style Die;
- 49-16-U002 #2 Aluminum U Style Die;
- 49-16-U001 #1 Aluminum U Style Die;
- 49-16-U01A 1/0 Aluminum U Style Die;
- 49-16-U02A 2/0 Aluminum U Style Die;
- 49-16-U03A 3/0 Aluminum U Style Die;
- 49-16-U04A 4/0 Aluminum U Style Die;
- 49-16-U250 250 MCM Aluminum U Style Die;
- 49-16-U300 300 MCM Aluminum U Style Die;
- 49-16-U350 350 MCM Aluminum U Style Die;

M18™ FORCE LOGIC™ 12T Utility Crimper Kit

2778-22

Specifications:

Output Force	12 Tons
Head Rotation	350°
Reporting and Tool Diagnostics	Built-In; ONE-KEY™ Compatible
Length	16"
Weight	11.9 lbs



Includes: (1) M18™ REDLITHIUM™ XC5.0 Extended Capacity Battery Pack, (1) M18™ REDLITHIUM™ 2.0 Compact Battery Pack, AC/DC Wall and Vehicle Charger, Carabiner, Utility Bag

M18™ FORCE LOGIC™ 750 MCM Crimper Kit

2779-22

Specifications:

Output Force	12 Tons
Head Rotation	350°
Reporting and Tool Diagnostics	Built-In; ONE-KEY™ Compatible
Length	16"
Weight	11.5 lbs



Includes: (1) M18™ REDLITHIUM™ XC5.0 Extended Capacity Battery Pack, (1) M18™ REDLITHIUM™ 2.0 Compact Battery Pack, Multi-Voltage Charger, Carrying Case

Related Accessories:

Accessory Kits

- 49-12-KITC EXACT™ #6 AWG – 750 MCM Cu 12T U Style Die Kit;
- 49-12-KITA EXACT™ #6 AWG – 750 MCM Al 12T U Style Die Kit

EXACT™ 12T Copper U Style Dies

- 49-12-U008C #8 Copper 12T U Style Die;
- 49-12-U006C #6 Copper 12T U Style Die;
- 49-12-U004C #4 Copper 12T U Style Die;
- 49-12-U002C #2 Copper 12T U Style Die;
- 49-12-U001C #1 Copper 12T U Style Die;
- 49-12-U01AC 1/0 Copper 12T U Style Die;
- 49-12-U02AC 2/0 Copper 12T U Style Die;
- 49-12-U03AC 3/0 Copper 12T U Style Die;
- 49-12-U04AC 4/0 Copper 12T U Style Die;
- 49-12-U250C 250 MCM Copper 12T U Style Die;
- 49-12-U300C 300 MCM Copper 12T U Style Die;
- 49-12-U350C 350 MCM Copper 12T U Style Die;
- 49-12-U400C 400 MCM Copper 12T U Style Die;
- 49-12-U500C 500 MCM Copper 12T U Style Die;
- 49-12-U600C 600 MCM Copper 12T U Style Die;
- 49-12-U750C 750 MCM Copper 12T U Style Die

EXACT™ 12T Aluminum U Style Dies

- 49-12-U008 #8 Aluminum 12T U Style Die;
- 49-12-U006 #6 Aluminum 12T U Style Die;
- 49-12-U004 #4 Aluminum 12T U Style Die;
- 49-12-U002 #2 Aluminum 12T U Style Die;
- 49-12-U001 #1 Aluminum 12T U Style Die;
- 49-12-U01A 1/0 Aluminum 12T U Style Die;
- 49-12-U02A 2/0 Aluminum 12T U Style Die;
- 49-12-U03A 3/0 Aluminum 12T U Style Die;
- 49-12-U04A 4/0 Aluminum 12T U Style Die;
- 49-12-U250 250 MCM Aluminum 12T U Style Die;
- 49-12-U300 300 MCM Aluminum 12T U Style Die;
- 49-12-U350 350 MCM Aluminum 12T U Style Die;
- 49-12-U400 400 MCM Aluminum 12T U Style Die;
- 49-12-U500 500 MCM Aluminum 12T U Style Die;
- 49-12-U600 600 MCM Aluminum 12T U Style Die;
- 49-12-U750 750 MCM Aluminum 12T U Style Die



M18™ FORCE LOGIC™ Cable Cutter Kit w/ 750 MCM Cu Jaws

2672-21

Specifications:

Capacity	750 MCM Cu, 1,000 MCM Al
Average Cut Speed	3 Seconds
Head Rotation	350°
Auto Reset	Yes
Length	14"

Includes: (1) M18™ REDLITHIUM™ 2.0 Compact Battery Pack, 750 MCM Cable Cutter Jaw, Allen Wrench, Multi-Voltage Charger, Carrying Case



M18™ FORCE LOGIC™ 3" Underground Cable Cutter Kit w/ Wireless Remote

2776R-21



Specifications:

Hydraulic Output Force	9 Tons
Cut Capacity	1500 MCM Cu 15KV
Tool Diagnostics	Built-In; ONE-KEY™ Compatible
Length	20-4/5"
Weight	15.75 lbs

Includes: (1) M18™ REDLITHIUM™ XC5.0 Extended Capacity Battery Pack, Remote, Carabiner, M18™ AC/DC Wall and Vehicle Charger, Utility Bag

Related Accessories:

49-16-2774 3" Underground Replacement Blades



M18™ FORCE LOGIC™ 10 Ton Knockout Tool Kit

2676-23, 2676-22 (2676-20 No Punches or Dies)

Specifications:

Mild Steel Capacity	6" in 12 Gauge
Stainless Steel Capacity	6" in 14 Gauge
Output Force	10 Ton
Quick-Connect Draw Stud	Yes
Weight	7.1 lbs
Height	5-1/2"

Includes: 2676-23 (2) M18™ REDLITHIUM™ XC Extended Capacity Battery Packs, EXACT™ 1/2" – 4" Conduit Punches and Dies, (3) Draw Studs, Quick Connect Alignment System, Multi-Voltage Charger, Carrying Case; 2676-22 Includes 1/2" – 2" EXACT™ Conduit Punches and Dies; 2676-20 Includes No Punches or Dies



M18™ FORCE LOGIC™ Press Tool Kit

2773-22 (2773-20 No Jaw Kit)

Specifications:

Capacity	1/2" – 4" (Varies by Material)
Weight	6.5 lbs
Length	14-1/10"
Calibration Interval	50,000 Cycles (LED Indicator)
Approximate Cycle Time	3.7 Seconds
Press Force	7,200 lbs

Includes: (2) M18™ REDLITHIUM™ 2.0 Compact Battery Packs, (6) Jaws (1/2", 3/4", 1", 1-1/4", 1-1/2", 2"), Multi-Voltage Charger, Carrying Case; 2773-20 Includes No Jaws



M18™ FORCE LOGIC™ Cable Cutter Kit w/ 477 ACSR Jaws

2672-21S

Specifications:

Capacity	477 HEN ACSR
Average Cut Speed	3 Seconds
Head Rotation	350°
Auto Reset	Yes
Length	14"

Includes: (1) M18™ REDLITHIUM™ 2.0 Compact Battery Pack, 477 ACSR Cutting Jaw, Carabiner, Allen Wrench, AC/DC Wall and Vehicle Charger, Bucket Bag



M18™ FORCE LOGIC™ 3" Underground Cable Cutter Kit

2776-21



Specifications:

Hydraulic Output Force	9 Tons
Cut Capacity	1500 MCM Cu 15KV
Tool Diagnostics	Built-In; ONE-KEY™ Compatible
Length	20-4/5"
Weight	15.75 lbs

Includes: (1) M18™ REDLITHIUM™ XC5.0 Extended Capacity Battery Pack, Carabiner, M18™ AC/DC Wall and Vehicle Charger, Utility Bag

Related Accessories:

49-16-2774 3" Underground Replacement Blades



M18™ FORCE LOGIC™ Knockout Accessories

Compatible with 2677-20 and 2676-20

EXACT™ Accessory Kits

49-16-2692 1/2" – 1-1/4" Knockout Set;
49-16-2693 1/2" – 2" Knockout Set;
49-16-2694 1/2" – 2" Hand Ratchet Knockout Set;
49-16-2695 2-1/2" – 4" Knockout Set

EXACT™ Punches and Dies

49-16-2660* 1/2" Die;
49-16-2660S 1/2" Die;
49-16-2661* 1/2" Punch;
49-16-2661S 1/2" Punch;
49-16-2662 3/4" Die;
49-16-2663 3/4" Punch;
49-16-2664 1" Die;
49-16-2665 1" Punch;
49-16-2666 1-1/4" Die;
49-16-2667 1-1/4" Punch;
49-16-2668 1-1/2" Die;
49-16-2669 1-1/2" Punch;
49-16-2670 2" Die;
49-16-2671 2" Punch;
49-16-2672 2-1/2" Die;
49-16-2673 2-1/2" Punch;
49-16-2674 3" Die;
49-16-2675 3" Punch;
49-16-2676 3-1/2" Die;
49-16-2677 3-1/2" Punch;
49-16-2678 4" Die;
49-16-2679 4" Punch;
49-16-2686 5" Die;
49-16-2687 5" Punch;
49-16-2688 6" Die;
49-16-2689 6" Punch

*These items are intended only for Mild Steel.

EXACT™ Sink Punches & Dies

49-16-2705 7/8" Sink Die;
49-16-2706 7/8" Sink Punch;
49-16-2700 1-3/8" Sink Die;
49-16-2701 1-3/8" Sink Punch

Draw Studs

49-16-2621 3/8" Ball Bearing Draw Stud;
49-16-2622 3/4" Ball Bearing Draw Stud;
49-16-2680 7/16" Draw Stud;
49-16-2681 3/4" Draw Stud;
49-16-2682 1-1/8" Draw Stud;
49-16-2707 1-1/8" Long Draw Stud

Adapters

49-16-2684 3/8" Adapter for EXACT™ 2-1/2" – 4" Dies to 3/4" Draw Studs;
49-16-2685 Adapter for M18™ FORCE LOGIC™ Knockout Tool to other major brands of punches and dies

M18™ FORCE LOGIC™ Long Throw Press Tool Kit

2673-22L (2673-20L No Jaw Kit)

Specifications:

Capacity	1/2" – 4" CU, 1/2" – 2" SS
Weight	10.1 lbs
Length	20-1/8"
Calibration Interval	40,000 Cycles (LED Indicator)
Approximate Cycle Time	5 Seconds, 10 Seconds at Full Stroke
Press Force	7,200 lbs

Includes: 2673-22L (2) M18™ REDLITHIUM™ XC Extended Capacity Battery Packs, (3) Jaws (1/2", 3/4", 1"), Multi-Voltage Charger, Carrying Case; 2673-20L Includes No Jaws



M18™ FORCE LOGIC™ Cable Cutter Accessories

Compatible with 2672-21 and 2672-21S

Cutter Jaws

49-16-2772 M18™ Cu/Al Cutting Jaw;
49-16-2773 M18™ ACSR Cutting Jaw

Cutter Replacement Blades

48-44-0411 Replacement Copper Blades;
48-44-0412 Replacement Steel Blades

M18™ FORCE LOGIC™ 1590 ACSR Cutter Kit

2777-21



Specifications:

Hydraulic Output Force	9 Tons
Cut Capacity	Up to 1590 Falcon ACSR
Tool Diagnostics	Built-In; ONE-KEY™ Compatible
Length	16-3/4"
Weight	11.75 lbs

Includes: (1) M18™ REDLITHIUM™ XC5.0 Extended Capacity Battery Pack, Carabiner, Side Handle, AC/DC Wall and Vehicle Charger, Utility Bag

Related Accessories:

49-16-2775 1590 ACSR Replacement Blades







M18™ FORCE LOGIC™ 6 Ton Knockout Tool Kit

2677-21 (2677-20 No Punches or Dies)

Specifications:

Mild Steel Capacity	4" in 14 Gauge
Stainless Steel Capacity	2" in 14 Gauge
Output Force	6 Ton
Quick-Connect Draw Stud	Yes
Weight	4.3 lbs
Height	4-1/2"

Includes: 2677-21 (1) M18™ REDLITHIUM™ 2.0 Compact Battery Pack, EXACT™ 1/2" – 2" Conduit Punches and Dies, (2) Draw Studs, Quick Connect Alignment System, Multi-Voltage Charger, Carrying Case; 2677-20 Includes No Punches or Dies



M18™ Short Throw Press Tool w/ PEX Crimp Jaws

2674-22C

Specifications:

Capacity	Up to 1"
Cycle Time	3 Seconds
Auto Cycle	Yes
Length	13-1/2"
Weight	4.8 lbs



Includes: (2) M18™ REDLITHIUM™ 2.0 Compact Battery Packs, (3) PEX Crimp Jaws (1/2", 3/4", 1"), Multi-Voltage Charger and Carrying Case

M18™ ProPEX® Expansion Tool Kit

2632-22XC (2632-20 Tool-Only)

Specifications:

Capacity	3/8" – 1-1/2"
Auto-Rotation	Built-In
Dimensions (L x W x H)	8-7/10" x 4-2/5" x 10-4/5"
Weight	9.2 lbs



Includes: (2) M18™ REDLITHIUM™ XC Extended Capacity Battery Packs, (3) ProPEX Expansion Heads (1", 1-1/4", 1-1/2"), Grease, Multi-Voltage Charger, Carrying Case

Related Accessories:

- 49-16-2608** 1" ProPEX® Expansion Head;
- 49-16-2610** 1-1/4" ProPEX® Expansion Head;
- 49-16-2612** 1-1/2" ProPEX® Expansion Head

M18™ Short Throw Press Tool w/ Viega PUREFLOW™ Jaws

2674-22P

Specifications:

Capacity	Up to 1"
Cycle Time	3 Seconds
Auto Cycle	Yes
Length	13-1/2"
Weight	4.8 lbs



Includes: (2) M18™ REDLITHIUM™ 2.0 Compact Battery Packs, (3) Viega PUREFLOW™ Jaws (1/2", 3/4", 1"), Multi-Voltage Charger, Carrying Case

M18™ Transfer Pump Kit

2771-21 (2771-20 Tool-Only)

Specifications:

Gallons Per Hour	480
Gallons Per Battery (XC)	144
Maximum Lift	18'
Maximum Head Height	75'
Self Priming	Yes
Flexible Impeller	Yes
Fittings	3/4" Brass Inlet and Outlet



Includes: (1) M18™ REDLITHIUM™ XC Battery, (2) 3/4" Brass Fittings, Multi-Voltage Charger

M18™ Short Throw Press Tool Accessories

Compatible with 2674-22C and 2674-22P

- 49-16-2630C** 3/8" PEX Crimp Jaw;
- 49-16-2631C** 1/2" PEX Crimp Jaw;
- 49-16-2632C** 5/8" PEX Crimp Jaw;
- 49-16-2633C** 3/4" PEX Crimp Jaw;
- 49-16-2634C** 1" PEX Crimp Jaw;
- 49-16-2630P** 3/8" Viega PUREFLOW™ Jaw;
- 49-16-2631P** 1/2" Viega PUREFLOW™ Jaw;
- 49-16-2632P** 5/8" Viega PUREFLOW™ Jaw;
- 49-16-2633P** 3/4" Viega PUREFLOW™ Jaw;
- 49-16-2634P** 1" Viega PUREFLOW™ Jaw

M18™ 2-Speed Grease Gun Kit

2646-22CT, 2646-21CT (2646-20 Tool-Only)

Specifications:

Output Pressure	Up to 10,000 PSI (690 BAR)
Run-Time	Up to 10 Cartridges Per Charge
Grease Capacity	14 oz Cartridge, 16 oz Bulk, 16 oz Suction
Air Bleeder Valve	Yes
Weight	8.5 lbs



Includes: 2646-22CT (2) M18™ REDLITHIUM™ Compact Battery Packs, 48" Flex Hose with Spring Guard, High Pressure Grease Coupler, Shoulder Strap, Multi-Voltage Charger, Carrying Case; 2646-21CT Includes (1) M18™ REDLITHIUM™ Compact Battery Pack

Related Accessories:

- 49-16-2646** M18™ Grease Gun 400g Clear Barrel;
- 49-16-2647** M18™ Replacement Grease Gun Hose with High Pressure Coupler;
- 49-16-2648** M18™ Right Angle Grease Gun Coupler;
- 49-16-2649** M18™ High Pressure Grease Coupler 2-Pack



M18™ FORCE LOGIC™ 2" - 3" ProPEX® Expansion Tool Kit

2633-22

Specifications:

Capacity	2", 2-1/2", and 3"
Auto-Rotation	Built-In
Auto-Cycle	Built-In
Dimensions (L x W x H)	14-1/2" x 11-4/5" x 4-3/4"
Weight	13.1 lbs



Includes: (2) M18™ REDLITHIUM™ XC4.0 Extended Capacity Battery Packs, (3) ProPEX® Expansion Heads (1/2", 2-1/2", 3"), Side Handle, Grease, Multi-Voltage Charger, Carrying Case

Related Accessories:

- 49-16-2614** 2" ProPEX® Expansion Head;
- 49-16-2616** 2-1/2" ProPEX® Expansion Head;
- 49-16-2618** 3" ProPEX® Expansion Head

M18™ 10 oz Caulk and Adhesive Gun Kit

2641-21CT (2641-20 Tool-Only)

Specifications:

Force	950 lbs
Inches Per Minute	0 – 21
Speed Settings	6
Auto-Reverse Anti-Drip	Yes
Weight	5.8 lbs



Includes: (1) M18™ REDLITHIUM™ Compact Battery Pack, 10 oz Carriage, M18™ 10 oz Plunger Rod and Piston Assembly, Multi-Voltage Charger

M18™ 20 oz Aluminum Barrel Sausage Style Caulk and Adhesive Gun Kit

2642-21CT

Specifications:

Force	950 lbs
Inches Per Minute	0 – 21
Speed Settings	6
Auto-Reverse Anti-Drip	Yes
Weight	6.5 lbs




Includes: (1) M18™ REDLITHIUM™ Compact Battery Pack, 20 oz Aluminum Sausage Style Barrel, M18™ 20 oz Plunger Rod and Piston Assembly, Nozzle, Multi-Voltage Charger

M18™ 20 oz Clear Barrel Sausage Style Caulk and Adhesive Gun Kit

2643-21CT

Specifications:

Force	950 lbs
Inches Per Minute	0 – 21
Speed Settings	6
Auto-Reverse Anti-Drip	Yes
Weight	6.6 lbs



Includes: (1) M18™ REDLITHIUM™ Compact Battery Pack, 20 oz Clear Sausage Style Barrel, M18™ 20 oz Plunger Rod and Piston Assembly, Nozzle, Multi-Voltage Charger

M18™ Caulk Gun Accessories

Compatible with 2641-21CT, 2642-21CT, and 2643-21CT

- 48-08-1076** M18™ 10 oz Caulk and Adhesive Gun Conversion Kit;
- 48-08-1093** M18™ 20 oz Aluminum Barrel Sausage Style Caulk and Adhesive Gun Conversion Kit;
- 48-08-1094** M18™ 20 oz Clear Barrel Sausage Style Caulk and Adhesive Gun Conversion Kit;
- 48-08-1095** M18™ Quart Caulk and Adhesive Gun Conversion Kit;
- 48-08-1091** 20 oz Aluminum Barrel Kit;
- 48-08-1096** 20 oz Clear Barrel Kit;
- 31-12-0700** Caulk Gun Nozzle – Black

M18™ ROCKET™ LED Tower Light

2130-20

Specifications:

Lumens	2,000 / 1,300 / 850
Modes	High, Medium, Low
Moisture Resistance	IP54
Height	40" Collapsed, 7' Fully Extended
Weight	16.2 lbs



Battery and Charger Sold Separately



M18™ ROCKET™ Tower Light/Charger

2135-21HD (2135-20 Tool-Only)

Specifications:

Lumens	3,000 / 1,700 / 900
Modes	High, Medium, Low
Moisture Resistance	IP54
Powered By	M18™ or Coded
Head	(3) Independent Multi-Directional
Height	41-1/2" Collapsed, 7' Fully Extended
Weight	18.0 lbs



Includes: (1) M18™ REDLITHIUM™ HIGH DEMAND™ 9.0 Battery Pack, Carrying Bag

POWERED BY CHARGES



M18™ RADIUS™ LED Compact Site Light w/ ONE-KEY™

2146-20

Specifications:

Lumens	4,400 / 2,100 / 1,000 (Customizable)
Modes	High, Medium, Low
Moisture Resistance	IP54
Powered By	M18™ or Coded
Hands Free	Self-Centering Metal Hook
Daisy Chain Compatible	Yes
Weight	10.6 lbs



Battery and Charger Sold Separately

Includes: Security Cable

POWERED BY CHARGES



M18™ RADIUS™ LED Compact Site Light

2145-20


Specifications:

Lumens	4,400 / 2,100 / 1,000
Modes	High, Medium, Low
Moisture Resistance	IP54
Powered By	M18™ or Corded
Hands Free	Self-Centering Metal Hook
Daisy Chain Compatible	Yes
Weight	10.6 lbs



Battery and Charger Sold Separately

Includes: Security Cable



M18™ LED Stick Light

2352-20

Specifications:

Lumens	300 / 150
Modes	High, Low
Moisture Resistance	IP54
Pivoting Head	45°
Hands Free	2 Stainless Steel Hooks
Length	11-5/8"
Weight	1.1 lbs



Battery and Charger Sold Separately



M18™ ROVER™ LED Dual Power Flood Light


2360-20

Specifications:

Lumens	3,000 / 1,500 / 650
Modes	High, Medium, Low
Powered By	M18™ or Corded
Hands Free	(3) Keyholes for Hanging
Length	9"
Weight	6.4 lbs



Battery and Charger Sold Separately



M18™ Lantern/Flood Light

2363-20

Specifications:

Lumens	700 / 350 / 70 / 700
Modes	High, Medium, Low, Strobe
Beam Pattern	Adjustable 180° – 360°
Moisture Resistance	IPX4
Hands Free	2 Stainless Steel Hooks
USB Charger	2.1A USB Charging Port
Length	11-1/2"
Weight	1.2 lbs



Battery and Charger Sold Separately



M18™ ROVER™ LED Flood Light

2361-20

Specifications:

Lumens	1,500 / 780
Modes	High, Low
Moisture Resistance	IP54
Hands-Free	(1) Keyhole for Hanging, (1) EMT Hanger
Length	8-3/4"
Weight	3.4 lbs



Battery and Charger Sold Separately



M18™ LED Search Light

2354-21 (2354-20 Tool-Only)

Specifications:

Lumens	1,250 / 1,200 / 600 / 1,200
Modes	Spot/Flood, Flood, Spot, Strobe
Beam Distance	730 yd / 667.5 m
Moisture Resistance	IP54
Head Rotation	198°
Length	11-1/2"
Weight	3.1 lbs



Includes: (1) M18™ REDLITHIUM™ XC5.0 Extended Capacity Battery Pack, Multi-Voltage Charger, Shoulder Strap



M18™ LED Work Light

2735-20

Specifications:

Lumens	100
Hands Free	Integrated Hook
Head Rotation	90°



Battery and Charger Sold Separately



M18™ LED Utility Bucket Light

2122-22HD, 2122-21HD (2122-20 Tool-Only)

Specifications:

Lumens	2,500 / 2,200 / 800
Modes	Flood, Spot/Flood, Spot
Hands Free	Patented Spring Loaded Bucket Clamp
Moisture Resistance	IP56
Length	13-3/4"
Weight	10.5 lbs



Includes: 2122-22HD (2) M18™ REDLITHIUM™ HIGH DEMAND™ 9.0 Battery Packs, Rapid Charger, Storage Bag; 2122-21HD Includes (1) M18™ REDLITHIUM™ HIGH DEMAND™ 9.0 Battery Pack



M18 FUEL™ String Trimmer Kit

2725-21HD (2725-20 Tool-Only)

Specifications:

Cutting Swath	14" – 16"
Line Diameter	.080" / .095"
RPM	0 – 4,600 / 0 – 5,800
Trigger	Variable Speed
Feed System	Bump Feed
Length	73-3/5"
Weight	12.3 lbs



Includes: (1) M18™ REDLITHIUM™ HIGH DEMAND™ 9.0 Battery Pack, Rapid Charger



M18 FUEL™ Hedge Trimmer Kit

2726-21HD (2726-20 Tool-Only)

Specifications:

Blade Length	24"
Cut Capacity	3/4"
SPM	3,400
Gear Case	All-Metal
Length	45-3/4"
Weight	10.9 lbs



Includes: (1) M18™ REDLITHIUM™ HIGH DEMAND™ 9.0 Battery Pack, Rapid Charger



M18 FUEL™ Blower Kit

2728-21HD (2728-20 Tool-Only)

Specifications:

Max Air Volume	450 CFM
Max Air Speed	100 MPH
Noise Rating (db)	63 (ANSI B175)
Cruise Control	Yes
Length	38-1/2"
Weight	8.1 lbs



Includes: (1) M18™ REDLITHIUM™ HIGH DEMAND™ 9.0 Battery Pack, Rapid Charger



M18™ Compact Blower

0884-20

Specifications:

Max Air Volume	100 CFM
Max Air Speed	160 MPH
Switch	3-Speed Electronic
Length	20-1/2"
Weight	2.6 lbs



Battery and Charger Sold Separately

Includes: Flexible Nozzle, 9" Extension, Universal Inflator/Deflator

M18™ Compact Vacuum

0882-20

Specifications:

Air Volume	40 CFM
Inlet Diameter	1-1/4"
Canister Volume	36 oz
Filter	HEPA
Weight	4.3 lbs



Battery and Charger Sold Separately

Includes: 4' Hose, (2) Extension Tools, Crevice Tool, Floor Tool, Removable HEPA Filter

Related Accessory: 49-90-1951 Filter

M18™ Wet/Dry Vacuum

0880-20

Specifications:

Material	Wet/Dry
Capacity	2 gal
Air Volume	45 CFM
Suction (H ₂ O)	32"
Washable Filter	Yes; HEPA
Compatibility	All MILWAUKEE® 18V Slide-On Batteries (LITHIUM-ION or NiCd)



Battery and Charger Sold Separately

Includes: HEPA Filter, Flexible Hose, Filter Assembly, Crevice Tool, Wide Utility Nozzle

Related Accessory: 49-90-1900 Filter

M18™ Jobsite Fan

0886-20

Specifications:

Max Air Flow	284 CFMs (18 MPH)
RPM (3 Settings)	1,370 / 1,900 / 2,350
Length	10-3/10"
Weight	5.2 lbs



Battery and Charger Sold Separately

Includes: AC Adapter

M18™ Radio Charger

2792-20

Specifications:

Modes	AM, FM, AUX, Bluetooth®
Battery Charger	Charges all M18™ Batteries
Bluetooth® Antenna	100 ft Range
USB Charging Port	2.1 Amps
Powered By	All M18™ Batteries, 120V AC



Battery Sold Separately

Includes: 16" Auxiliary Input Cord, (2) AAA Batteries (For Memory Backup)

CHARGES



M18™ Jobsite Radio

2890-20

Specifications:

Modes	AM, FM, AUX
Tuner	Digital Processor w/ 10 Station Presets
USB Charging Port	2.1 Amps
Device Storage	Weather Sealed Auxiliary Compartment
Powered By	All M18™ Batteries, 120V AC



Battery and Charger Sold Separately

Includes: 6" Auxiliary Cord, (2) AAA Batteries (For Memory Backup)

M18™ / M12™ Wireless Jobsite Speaker

2891-20

Specifications:

Modes	Bluetooth, AUX (Cable Not Included)
Bluetooth Range	100 ft
USB Charging Port	2.1 Amp
Powered By	All M18™ and M12™ Batteries



Battery and Charger Sold Separately

Includes: AC Adapter

M18™ Power Source

49-24-2371

Specifications:

Powered By	All M18™ Batteries
Run-Time	Up to 18 Hours
2.1 Amp USB Port	Universal Charging for Smartphones, Tablets and Other Portable Electronic Devices



Battery Sold Separately

Powers all MILWAUKEE® M12™ Heated Gear



M18™ REDLITHIUM™ HIGH DEMAND™ 9.0 System Starter Kit

48-59-1890

Includes: (1) M18™ REDLITHIUM™ HIGH DEMAND™ 9.0 Battery Pack, Rapid Charger



M18™ REDLITHIUM™ XC5.0 System Starter Kit

48-59-1850

Includes: (1) M18™ REDLITHIUM™ XC5.0 Battery Pack, Multi-Voltage Charger



M18™ REDLITHIUM™ XC System Starter Kit

48-59-1813

Includes: (1) M18™ REDLITHIUM™ XC Battery Pack, Multi-Voltage Charger



M18™ and M12™ Multi-Voltage Charger

48-59-1812

Specifications:

Compatibility	All M18™ and M12™ Batteries
Charge Sequence	Sequential (First In, First Charged)
Integrated Hang-Holes	Yes
On-Board Indicator Light	Yes
Cell Voltage Monitoring	Yes



Batteries Sold Separately

M18™ and M12™ Rapid Charge Station

48-59-1807

Specifications:

Compatibility	All M18™ and M12™ Batteries
Charge Sequence	Charges 3 Batteries Simultaneously
Charge Speed	Charges Individual Batteries up to 40% Faster
Capacity	Holds (3) M18™ and (3) M12™ Batteries
Integrated Hang-Holes	Yes
Cell Voltage Monitoring	Yes
Pass-Through Plug	Yes



Batteries Sold Separately

Pass-Through Plug

M18™ and M12™ Rapid Charger

48-59-1808

Specifications:

Compatibility	All M18™ and M12™ Batteries
Charge Sequence	Sequential (First In, First Charged)
Charge Speed	Charges Individual Batteries up to 40% Faster
On-Board Indicator Light	Yes
Integrated Hang-Holes	Yes
Cell Voltage Monitoring	Yes



Batteries Sold Separately

M18™ Six-Pack Sequential Charger

48-59-1806

Specifications:

Compatibility	All M18™ Batteries
Charge Sequence	Sequential (Counter-Clockwise Rotation)
Skip Button	Manually Designate which Battery Charges First
Integrated Hang-Holes	Yes
Cell Voltage Monitoring	Yes
Pass-Through Plug	Yes



Batteries Sold Separately

Pass-Through Plug

M18™ AC/DC Wall and Vehicle Charger

2710-20

Specifications:

Compatibility	All M18™ Batteries
Integrated Hang-Holes	Yes
On-Board Indicator Light	Yes
Cell Voltage Monitoring	Yes



FULL SYSTEM COMPATIBILITY

- COMPACT**
 - Less weight and smaller size for light drilling and fastening
- EXTENDED CAPACITY**
 - More power and run-time, great performance for all demands
- HIGH DEMAND™**
 - Best performance for high demand applications



← LIGHT APPLICATIONS **OPTIMIZING PERFORMANCE AT EVERY LEVEL** HEAVY APPLICATIONS →
All M18™ REDLITHIUM™ batteries are compatible with all M18™ tools

COMPACT

- Lighter weight for less fatigue
- Compact size for increased versatility

EXTENDED CAPACITY

- Double the run-time of compact packs
- Increased performance and power

HIGH DEMAND

- Double the run-time of XC packs
- Highest power output
- Runs coolest in heavy application

M18™ REDLITHIUM™ 2.0 Compact Battery Pack
48-11-1820



M18™ REDLITHIUM™ XC6.0 Extended Capacity Battery Pack
48-11-1860



M18™ REDLITHIUM™ HIGH DEMAND™ 9.0 Battery Pack
48-11-1890



M18™ REDLITHIUM™ Compact Battery Pack
48-11-1815
2-Pack Available
48-11-1811



M18™ REDLITHIUM™ XC5.0 Extended Capacity Battery Pack
48-11-1850
2-Pack Available
48-11-1852



M18™ REDLITHIUM™ XC4.0 Extended Capacity Battery Pack
48-11-1840
10-Pack Available
48-11-1841



M18™ REDLITHIUM™ XC Extended Capacity Battery Pack
48-11-1828
2-Pack Available
48-11-1822



UP TO **5X** MORE RUN-TIME
UP TO **35%** MORE POWER
RUNS UP TO **60%** COOLER



M18™ COMBO KITS

Kit Tool Total	2 PIECE KITS											4 PIECE KITS				LARGE KITS							
	2796-22	2897-22	2799-22CX	2697-22	2697-22CT	2795-22	2798-22CT	2691-22	2894-22	2694-22	2695-22	2899-22	2896-22	2896-22CT	2896-24	2694-24	2695-24	2696-24	2896-26	2696-26	2696-29	2695-15	
M18 FUEL™ 1/2" Hammer Drill/Driver w/ ONE-KEY™	■																						
M18 FUEL™ 1/2" Hammer Drill/Driver		■							■						■								
M18™ 1/2" Compact Brushless Hammer Drill/Driver			■																				
M18™ 1/2" Compact Hammer Drill/Driver				■	■					■	■					■	■	■		■	■	■	■
M18 FUEL™ 1/2" Drill/Driver w/ ONE-KEY™						■																	
M18 FUEL™ 1/2" Drill/Driver																							
M18™ 1/2" Compact Brushless Drill/Driver							■																
M18™ 1/2" Compact Drill/Driver								■															
M18™ 3/8" Right Angle Drill/Driver																					■	■	
M18 FUEL™ Drywall Screw Gun												■	■										
M18 FUEL™ 1/4" Hex Impact Driver w/ ONE-KEY™	■					■																	
M18 FUEL™ SURGE™ 1/4" Hex Hydraulic Driver											■	■	■										
M18 FUEL™ 1/4" Hex Impact Driver		■												■									
M18™ 1/4" Hex Brushless Impact Driver			■				■																
M18™ 1/4" Hex Impact Driver*				■	■			■													■	■	■
M18™ 5/8" SDS Plus Rotary Hammer																							■
M18™ 1/2" High Torque Impact Wrench																							■
M18™ 1/2" Compact Impact Wrench																							■
M18 FUEL™ SAWZALL® Recip Saw									■						■								■
M18™ SAWZALL® Recip Saw										■						■							■
M18™ HACKZALL® One-Handed Recip Saw											■												■
M18 FUEL™ 6-1/2" Circular Saw																							■
M18™ 6-1/2" Circular Saw																							■
M18™ Jig Saw																							■
M18™ Multi-Tool																							■
M18™ Band Saw																							■
M18™ 5-3/8" Metal Cutting Saw																							■
M18 FUEL™ 4-1/2" / 5" Grinder Paddle Switch, No-Lock Kit																							■
M18™ 4-1/2" Cut-Off / Grinder																							■
M18™ Compact Blower																							■
M18™ LED Work Light																							■
Also Includes																							
M18™ and M12™ Multi-Voltage Charger	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■
M18™ Six-Pack Sequential Charger																							■
M18™ REDLITHIUM™ Compact Battery Pack					2		2																
M18™ REDLITHIUM™ 2.0 Compact Battery Pack			1				2						2										
M18™ REDLITHIUM™ XC Extended Capacity Battery Pack				2						2				2	2	2			2	2			
M18™ REDLITHIUM™ XC4.0 Extended Capacity Battery Pack			1																				4
M18™ REDLITHIUM™ XC5.0 Extended Capacity Battery Pack	2	2				2			2	2		2	2						2				
Carrying Case	■	■				■																	
Contractor Bag			■	■	■		■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■	■

*M18™ 1/4" Hex Impact Driver is the single, variable speed model



PORTABLE POWER TOOL LIMITED WARRANTY

Every MILWAUKEE **power tool*** (see exceptions below) is warranted to the **original purchaser only** to be free from defects in material and workmanship. Subject to certain exceptions, MILWAUKEE will repair or replace any part on an electric power tool which, after examination, is determined by MILWAUKEE to be defective in material or workmanship for a period of five (5) years** after the date of purchase unless otherwise noted. Return of the power tool to a MILWAUKEE factory Service Center location or MILWAUKEE Authorized Service Station, freight prepaid and insured, is required. A copy of the proof of purchase should be included with the return product. This warranty does not apply to damage that MILWAUKEE determines to be from repairs made or attempted by anyone other than MILWAUKEE authorized personnel, misuse, alterations, abuse, normal wear and tear, lack of maintenance, or accidents.

Normal Wear: Many power tools need periodic parts replacement and service to achieve best performance. This warranty does not cover repair when normal use has exhausted the life of a part including, but not limited to, chucks, brushes, cords, saw shoes, blade clamps, o-rings, seals, bumpers, driver blades, pistons, strikers, lifters, and bumper cover washers.

*This **warranty** does not cover Air Nailers & Staplers; Airless Paint Sprayer; Cordless Battery Packs; Gasoline Driven Portable Power Generators; Hand Tools; Hoist – Electric, Lever & Hand Chain; M12™ Heated Gear; Reconditioned Product; and Test & Measurement Products. **There are separate and distinct warranties** available for these products.

The warranty period for **Job Site Radios, M12™ Power Port, M18™ Power Source, Jobsite Fan and Trade Titan™ Industrial Work Carts is **one (1) year** from the date of purchase. The warranty period for the **Drain Cleaning Cables** is **two (2) years** from the date of purchase. The warranty period for the **LED** in the LED Work Light and the **LED Upgrade Bulb** for the Work Light is the **lifetime** of the product subject to the limitations above. If during normal use the LED or LED Bulb fails, the part will be replaced free of charge.

Warranty Registration is not necessary to obtain the applicable warranty on a MILWAUKEE power tool product. The manufacturing date of the product will be used to determine the warranty period if no proof of purchase is provided at the time warranty service is requested.

ACCEPTANCE OF THE EXCLUSIVE REPAIR AND REPLACEMENT REMEDIES DESCRIBED HEREIN IS A CONDITION OF THE CONTRACT FOR THE PURCHASE OF EVERY MILWAUKEE PRODUCT. IF YOU DO NOT AGREE TO THIS CONDITION, YOU SHOULD NOT PURCHASE THE PRODUCT. IN NO EVENT SHALL MILWAUKEE BE LIABLE FOR ANY INCIDENTAL, SPECIAL, CONSEQUENTIAL OR PUNITIVE DAMAGES, OR FOR ANY COSTS, ATTORNEY FEES, EXPENSES, LOSSES OR DELAYS ALLEGED TO BE AS A CONSEQUENCE OF ANY DAMAGE TO, FAILURE OF, OR DEFECT IN ANY PRODUCT INCLUDING, BUT NOT LIMITED TO, ANY CLAIMS FOR LOSS OF PROFITS. SOME STATES DO NOT ALLOW THE EXCLUSION OR LIMITATION OF INCIDENTAL OR CONSEQUENTIAL DAMAGES, SO THE ABOVE LIMITATION OR EXCLUSION MAY NOT APPLY TO YOU. THIS WARRANTY IS EXCLUSIVE AND IN LIEU OF ALL OTHER EXPRESS WARRANTIES, WRITTEN OR ORAL. TO THE EXTENT PERMITTED BY LAW, MILWAUKEE DISCLAIMS ANY IMPLIED WARRANTIES, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR USE OR PURPOSE; TO THE EXTENT SUCH DISCLAIMER IS NOT PERMITTED BY LAW, SUCH IMPLIED WARRANTIES ARE LIMITED TO THE DURATION OF THE APPLICABLE EXPRESS WARRANTY AS DESCRIBED ABOVE. SOME STATES DO NOT ALLOW LIMITATIONS ON HOW LONG AN IMPLIED WARRANTY LASTS, SO THE ABOVE LIMITATION MAY NOT APPLY TO YOU, THIS WARRANTY GIVES YOU SPECIFIC LEGAL RIGHTS, AND YOU MAY ALSO HAVE OTHER RIGHTS WHICH VARY FROM STATE TO STATE.

This warranty applies to product sold in the U.S.A. and Canada only.

Please consult the **‘Service Center Search’** in the **Parts & Service** section of MILWAUKEE’s website www.milwaukeeetool.com or call 1.800.SAWDUST (1.800.729.3878) to locate your nearest service facility for warranty and non-warranty service on a Milwaukee **electric power tool**.

CORDLESS BATTERY PACK LIMITED WARRANTY

Every MILWAUKEE Battery Pack (sold with cordless product and/or as a replacement battery pack) is warranted to the original purchaser only to be free from defects in material and workmanship. Subject to certain exceptions, MILWAUKEE will repair or replace a battery pack which, after examination, is determined by MILWAUKEE to be defective in material or workmanship for the stated warranty period from date of purchase. Return of the battery pack to a MILWAUKEE factory Service Center location or MILWAUKEE Authorized Service Station, freight prepaid and insured, is required. For the proper shipping procedure of battery packs, contact 1.800.SAWDUST (1.800.729.3878), or go to www.milwaukeeetool.com. A copy of the proof of purchase should be included with the return product. This warranty does not apply to damage that MILWAUKEE determines to be from repairs made or attempted by anyone other than MILWAUKEE authorized personnel, misuse, alterations, abuse, normal wear and tear, lack of maintenance, or accidents.

Battery Pack Cat. No.	Chemistry	Warranty Period (from date of purchase)
48-11-1828 (Serial number prefix "B41E" and later) 48-11-1840 48-11-1850 48-11-1860 48-11-1890 48-11-2402 48-11-2440 48-11-2460 48-11-2830 (Serial number prefix "C71")	LITHIUM-ION	Three (3) Years
48-11-0490 48-11-1815 48-11-1820 48-11-2001 48-11-2401 48-11-2420 48-11-2430	LITHIUM-ION	Two (2) Years
48-11-1828 (Serial number prefix "B41D" and earlier) 48-11-1830 (Serial number prefix "A95") 48-11-2830 (Serial number prefix "A71")	LITHIUM-ION	Two (2) Years – plus, Three (3) Years Pro-Rata (prorated)*
48-11-0100 48-11-1024 48-11-1830 (Serial number prefix "E95") 48-11-1970 48-11-2230	Nickel-Cadmium (Ni-Cd), Nickel-Metal-Hydride (Ni-MH), LITHIUM-ION	One (1) Year

*The warranty period for MILWAUKEE M18™ 48-11-1828 (with the serial number prefix "B41D" and earlier), V18™ 48-11-1830 (with the serial number prefix "A95"), and V28™ 48-11-2830 (with the serial number prefix "A71") is five (5) years / 2000 charges from the date of purchase, whichever first occurs. The first 1000 charges or 2 years of the warranty, whichever first occurs, are covered through free replacement of the defective battery. This means that for the earlier of the first 1000 charges or two (2) years from the date of purchase/first charge, a replacement battery will be provided to the customer for any defective battery free of charge. Thereafter, the remaining charges up to a total of 2000 or the remainder of the five (5) year period from the date of purchase, whichever first occurs, will be covered on a pro rata basis. This means that every customer gets an additional 1000 charges or three (3) years of pro rata warranty on the these battery packs, depending upon the amount of use. MILWAUKEE M18™ 48-11-1828 (with the serial number prefix "B41E" and later), V18™ 48-11-1830 (with the serial number prefix "E95"), and M28™ 48-11-2830 (with the serial number prefix "C71") have different warranty periods, as listed.

Warranty Registration is not necessary to obtain the applicable warranty on a MILWAUKEE battery pack. The manufacturing date of the product will be used to determine the warranty period if no proof of purchase is provided at the time warranty service is requested.

ACCEPTANCE OF THE EXCLUSIVE REPAIR AND REPLACEMENT REMEDIES DESCRIBED HEREIN IS A CONDITION OF THE CONTRACT FOR THE PURCHASE OF EVERY MILWAUKEE PRODUCT. IF YOU DO NOT AGREE TO THIS CONDITION, YOU SHOULD NOT PURCHASE THE PRODUCT. IN NO EVENT SHALL MILWAUKEE BE LIABLE FOR ANY INCIDENTAL, SPECIAL, CONSEQUENTIAL OR PUNITIVE DAMAGES, OR FOR ANY COSTS, ATTORNEY FEES, EXPENSES, LOSSES OR DELAYS ALLEGED TO BE AS A CONSEQUENCE OF ANY DAMAGE TO, FAILURE OF, OR DEFECT IN ANY PRODUCT INCLUDING, BUT NOT LIMITED TO, ANY CLAIMS FOR LOSS OF PROFITS. SOME STATES DO NOT ALLOW THE EXCLUSION OR LIMITATION OF INCIDENTAL OR CONSEQUENTIAL DAMAGES, SO THE ABOVE LIMITATION OR EXCLUSION MAY NOT APPLY TO YOU. THIS WARRANTY IS EXCLUSIVE AND IN LIEU OF ALL OTHER EXPRESS WARRANTIES, WRITTEN OR ORAL. TO THE EXTENT PERMITTED BY LAW, MILWAUKEE DISCLAIMS ANY IMPLIED WARRANTIES, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR USE OR PURPOSE; TO THE EXTENT SUCH DISCLAIMER IS NOT PERMITTED BY LAW, SUCH IMPLIED WARRANTIES ARE LIMITED TO THE DURATION OF THE APPLICABLE EXPRESS WARRANTY AS DESCRIBED ABOVE. SOME STATES DO NOT ALLOW LIMITATIONS ON HOW LONG AN IMPLIED WARRANTY LASTS, SO THE ABOVE LIMITATION MAY NOT APPLY TO YOU, THIS WARRANTY GIVES YOU SPECIFIC LEGAL RIGHTS, AND YOU MAY ALSO HAVE OTHER RIGHTS WHICH VARY FROM STATE TO STATE.

This warranty applies to product sold in the U.S.A. and Canada only.

Please consult the **‘Service Center Search’** in the **Parts & Service** section of MILWAUKEE’s website www.milwaukeeetool.com or call 1.800.SAWDUST (1.800.729.3878) to locate your nearest service facility for warranty and non-warranty service on a MILWAUKEE Battery Pack.

HEATED GEAR LIMITED WARRANTY

Every **MILWAUKEE M12 HEATED JACKET** (including its battery holder) is warranted to the **original purchaser only** to be free from defects in material and workmanship. Subject to certain exceptions, MILWAUKEE will repair or replace any part on M12™ Heated Jacket which, after examination, is determined by MILWAUKEE to be defective in material or workmanship for a period of one (1) year* after the date of purchase. Return of the Heated Jacket to a MILWAUKEE factory Service Center location, freight prepaid and insured, is required. A copy of the proof of purchase should be included with the return product. This warranty does not apply to damage that MILWAUKEE determines to be from repairs made or attempted by anyone other than MILWAUKEE personnel, misuse, alterations, abuse, normal wear and tear, or accidents.

*This warranty does not cover a M12™ LITHIUM-ION Battery Pack; **there is a separate and distinct warranty** available for a battery pack.

Warranty Registration is not necessary to obtain the applicable warranty on a MILWAUKEE heated jacket. The manufacturing date of the product will be used to determine the warranty period if no proof of purchase is provided at the time warranty service is requested.

ACCEPTANCE OF THE EXCLUSIVE REPAIR AND REPLACEMENT REMEDIES DESCRIBED HEREIN IS A CONDITION OF THE CONTRACT FOR THE PURCHASE OF EVERY MILWAUKEE PRODUCT. IF YOU DO NOT AGREE TO THIS CONDITION, YOU SHOULD NOT PURCHASE THE PRODUCT. IN NO EVENT SHALL MILWAUKEE BE LIABLE FOR ANY INCIDENTAL, SPECIAL, CONSEQUENTIAL OR PUNITIVE DAMAGES, OR FOR ANY COSTS, ATTORNEY FEES, EXPENSES, LOSSES OR DELAYS ALLEGED TO BE AS A CONSEQUENCE OF ANY DAMAGE TO, FAILURE OF, OR DEFECT IN ANY PRODUCT INCLUDING, BUT NOT LIMITED TO, ANY CLAIMS FOR LOSS OF PROFITS. SOME STATES DO NOT ALLOW THE EXCLUSION OR LIMITATION OF INCIDENTAL OR CONSEQUENTIAL DAMAGES, SO THE ABOVE LIMITATION OR EXCLUSION MAY NOT APPLY TO YOU. THIS WARRANTY IS EXCLUSIVE AND IN LIEU OF ALL OTHER EXPRESS WARRANTIES, WRITTEN OR ORAL. TO THE EXTENT PERMITTED BY LAW, MILWAUKEE DISCLAIMS ANY IMPLIED WARRANTIES, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR USE OR PURPOSE; TO THE EXTENT SUCH DISCLAIMER IS NOT PERMITTED BY LAW, SUCH IMPLIED WARRANTIES ARE LIMITED TO THE DURATION OF THE APPLICABLE EXPRESS WARRANTY AS DESCRIBED ABOVE. SOME STATES DO NOT ALLOW LIMITATIONS ON HOW LONG AN IMPLIED WARRANTY LASTS, SO THE ABOVE LIMITATION MAY NOT APPLY TO YOU, THIS WARRANTY GIVES YOU SPECIFIC LEGAL RIGHTS, AND YOU MAY ALSO HAVE OTHER RIGHTS WHICH VARY FROM STATE TO STATE.

THIS WARRANTY GIVES YOU SPECIFIC LEGAL RIGHTS, AND YOU MAY ALSO HAVE OTHER RIGHTS WHICH VARY FROM STATE TO STATE.

This warranty applies to product sold in the U.S.A. and Canada only.

Please consult the **‘Service Center Search’** in the **Parts & Service** section of MILWAUKEE’s website www.milwaukeeetool.com or call 1.800.SAWDUST (1.800.729.3878) to locate your nearest MILWAUKEE **factory** Service Center location.

OUTDOOR POWER EQUIPMENT LIMITED WARRANTY

Every MILWAUKEE **Outdoor Power Equipment Product*** (see exceptions below) is warranted to the **original purchaser only** to be free from defects in material and workmanship. Subject to certain exceptions, MILWAUKEE will repair or replace any part on an outdoor power equipment product which, after examination, is determined by MILWAUKEE to be defective in material or workmanship for a period of three (3) years after the date of purchase unless otherwise noted. Return of the outdoor power equipment to a MILWAUKEE factory Service Center location or participating MILWAUKEE Authorized Service Station, freight prepaid and insured, is required. A copy of the proof of purchase should be included with the return product. This warranty does not apply to damage that MILWAUKEE determines to be from repairs made or attempted by anyone other than MILWAUKEE authorized personnel, misuse, alterations, abuse, normal wear and tear, lack of maintenance, or accidents.

Normal Wear: Many outdoor power equipment products need periodic parts replacement and service to achieve best performance. This warranty does not cover repair when normal use has exhausted the life of a part including, but not limited to trimmer head, trimmer head spool, cutting lines, blades, chains, blower tubes, brushes, o-rings, and seals.

*This **warranty** does not cover Cordless Battery Packs or Reconditioned Product. **There are separate and distinct warranties** available for these products.

MILWAUKEE does **not** cover freight or labor charges associated with the inspection and testing of **outdoor power equipment products** which are found by MILWAUKEE **not** to be a valid warranty claim. A valid warranty claim **must be substantiated** by the discovery of defective material or workmanship by MILWAUKEE.

ACCEPTANCE OF THE EXCLUSIVE REPAIR AND REPLACEMENT REMEDIES DESCRIBED HEREIN IS A CONDITION OF THE CONTRACT FOR THE PURCHASE OF EVERY MILWAUKEE PRODUCT. IF YOU DO NOT AGREE TO THIS CONDITION, YOU SHOULD NOT PURCHASE THE PRODUCT. IN NO EVENT SHALL MILWAUKEE BE LIABLE FOR ANY INCIDENTAL, SPECIAL, CONSEQUENTIAL OR PUNITIVE DAMAGES, OR FOR ANY COSTS, ATTORNEY FEES, EXPENSES, LOSSES OR DELAYS ALLEGED TO BE AS A CONSEQUENCE OF ANY DAMAGE TO, FAILURE OF, OR DEFECT IN ANY PRODUCT INCLUDING, BUT NOT LIMITED TO, ANY CLAIMS FOR LOSS OF PROFITS. SOME STATES DO NOT ALLOW THE EXCLUSION OR LIMITATION OF INCIDENTAL OR CONSEQUENTIAL DAMAGES, SO THE ABOVE LIMITATION OR EXCLUSION MAY NOT APPLY TO YOU. THIS WARRANTY IS EXCLUSIVE AND IN LIEU OF ALL OTHER EXPRESS WARRANTIES, WRITTEN OR ORAL. TO THE EXTENT PERMITTED BY LAW, MILWAUKEE DISCLAIMS ANY IMPLIED WARRANTIES, INCLUDING WITHOUT LIMITATION ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR USE OR PURPOSE; TO THE EXTENT SUCH DISCLAIMER IS NOT PERMITTED BY LAW, SUCH IMPLIED WARRANTIES ARE LIMITED TO THE DURATION OF THE APPLICABLE EXPRESS WARRANTY AS DESCRIBED ABOVE. SOME STATES DO NOT ALLOW LIMITATIONS ON HOW LONG AN IMPLIED WARRANTY LASTS, SO THE ABOVE LIMITATION MAY NOT APPLY TO YOU, THIS WARRANTY GIVES YOU SPECIFIC LEGAL RIGHTS, AND YOU MAY ALSO HAVE OTHER RIGHTS WHICH VARY FROM STATE TO STATE.

This warranty applies to product sold in the U.S.A. and Canada only.

Please consult the **‘Service Center Search’** in the **Parts & Service** section of MILWAUKEE’s website www.milwaukeeetool.com or call 1.800.SAWDUST (1.800.729.3878) to locate your nearest service facility for warranty and non-warranty service on a Milwaukee **electric power tool**.

LIGHTNING MAX REPAIR

MILWAUKEE® understands the unpredictability of the jobsite and the need for fast, reliable repairs and replacements. Through our Lightning Max Repair Program we are committed to providing you the best service so you can minimize downtime and get the job done.

SPEED: Repair of your tool in 7 – 10 days

PAY LESS, NOT MORE: Guaranteed to never pay more than the quoted Lightning Max Repair price

RELIABILITY: All repairs are serviced by experienced, certified factory technicians

QUALITY: Only genuine MILWAUKEE® parts used

WHERE TO GO FOR LIGHTNING MAX REPAIRS

eSERVICE

Solution for quick, convenient repairs, best for smaller tool quantities.

- Fedex shipping to MILWAUKEE® repair facility
- Your tool returned directly to you – No need to pick it up
- Go to www.milwaukeetool.com/eService

FACTORY SERVICE CENTERS

Factory Service Centers also carry the widest variety of MILWAUKEE® Tools and Accessories for all your needs.
1-800-SAWDUST (1-800-729-3878)

Anaheim

1130 N Magnolia
Anaheim, CA 92801

Atlanta

6155 Jimmy Carter Blvd
Suite F2
Norcross, GA 30071

Boston

375 University Avenue
Westwood, MA 02090

Chicago

6310 Gross Point Road
Niles, IL 60714

Cleveland

8200 Sweet Valley Drive
Valley View, OH 44125

Dallas

1625 W Mockingbird Ln
Unit 205
Dallas, TX 75235

Denver

2500 W 8th Avenue, Unit E
Denver, CO 80204

Houston

3566 West T.C. Jester Blvd
Houston, TX 77018

Las Vegas

5580 S Decatur Blvd
Unit 110
Las Vegas, NV 89118

Miami

3311 NW 82nd Avenue
Miami, FL 33122

Minneapolis/St. Paul

9705 Valley View Road
Eden Prairie, MN 55344

Milwaukee

13145 W Lisbon Road
Brookfield, WI 53005

New York City

3068 Whitestone Expressway
Flushing, NY 11354

Philadelphia

711 West Chester Pike
Havertown, PA 19064

San Antonio

14329 San Pedro Avenue, Suite D
San Antonio, TX 78232

San Diego

7849 -7851 Clairemont Mesa Blvd.
San Diego, CA 92111

San Francisco/Oakland

2341 Lincoln Avenue
Hayward, CA 94545

Seattle

5963 Corson Avenue South
Suite 104
Seattle, WA 98108

Washington D.C.

11900 Baltimore Ave
Suite B
Beltsville, MD 20705

CANADA

1-800-268-4015

Edmonton

14506 – 115th Avenue NW
Edmonton AB T5M 3B9

Halifax

Unit 102 50 Akerley Blvd
Dartmouth NS B3B 1R8

Saskatoon

Unit 630 3530 Millar Ave
Saskatoon SK S7P 0B3

Vancouver

9000 Bill Fox Way, Unit 103A
Burnaby BC V5J 5J3

Vaughan

140 Fernstaff Court, Unit 4
Vaughan ON L4K 3L8

Winnipeg

675 Berry St, Unit H
Winnipeg MB R3H 1A7

SYSTEMS

M12™ System	9
M18™ System	27

DRILLING & DRIVING

M12™ Screwdrivers	13
M12™ Hammer Drill/Drivers	13
M12™ Drill/Drivers	13
M12™ Right Angle Drill	13
M18™ Hammer Drill/Drivers	31
M18™ Drill/Drivers	31
M18™ Right Angle Drills	32
M18™ Drywall Screw Gun	32
M18™ HOLE HAWG® / SUPER HAWG™ Right Angle Drills	33
M18™ Magnetic Drills	33

CONCRETE

M12™ Rotary Hammers	15
M12™ HAMMERVAC™ Universal Dust Extractor	15
M18™ Rotary Hammers	34
M18™ HAMMERVAC™ Dust Extractors	34

IMPACTS & FASTENING

M12™ Impact Drivers	13
M12™ Right Angle Impact Driver	14
M12™ Impact Wrenches	14
M12™ Ratchets	14
M18™ Impact Drivers	35
M18™ Impact Wrenches	36
M18™ Right Angle Impact Driver	37
M18™ Right Angle Impact Wrench	37
M18™ Mid-Torque Impact Wrenches	37
M18™ High Torque Impact Wrenches	38

SAWING & CUTTING

M12™ Circular Saw	16
M12™ HACKZALL® Recip Saws	16
M12™ Jig Saw	16
M12™ Multi-Tool	16
M12™ Rotary Tool	17
M18™ SAWZALL® / HACKZALL® Recip Saws	39
M18™ Circular Saws	40
M18™ Planer	40
M18™ Jig Saw	40
M18™ Multi-Tool	41
M18™ Cut Out Tool	41
M18™ Miter Saw	42
M18™ Nailers	42

METAL WORKING

M12™ Band Saw	16
M18™ Band Saws	41
M18™ Metal Cutting Saw	41
M18™ Cut-Off / Grinders	43
M18™ Die Grinder	44
M18™ Shears	44

PLUMBING & ELECTRICAL

M12™ Plastic Pipe Sheer	17
M12™ Copper Tubing Cutter	17
M12™ 600 MCM Cable Cutter	17
M12™ Drain Snake	17
M12™ TRAPSNAKE™ Augers	17
M12™ ProPEX® Expansion Tool	18
M12™ Press Tool	18
M12™ No-Hub Driver	18
M18™ Press Tools	48
M18™ ProPEX® Expansion Tools	49
M18™ Transfer Pump	49
M18™ Crimpers / Accessories	45
M18™ Cable Cutters / Accessories	47
M18™ Knockout Tools	47

APPLICATORS

M12™ Caulk Guns / Accessories	18
M12™ Grease Gun	19
M18™ Grease Gun	49
M18™ Caulk Guns / Accessories	50

TEST & MEASUREMENT

M12™ M-SPECTOR FLEX™ / Accessories	19
M12™ M-SPECTOR 360™ / Accessories	20
M12™ Infrared Cameras	20
M12™ TEMP-GUN™	20

SPECIALTY PRODUCTS

M12™ Palm Nailer	15
M12™ Spot Polisher	15
M12™ LED Lights	21
M12™ Heated Gear / Accessory	22
M12™ Power Source	23
M12™ Vacuum	23
M12™ Jobsite Speaker	23
M12™ Jobsite Radio	23
M18™ Polisher	43
M18™ LED Lights	50
M18™ String Trimmer	52
M18™ Hedge Trimmer	52
M18™ Blowers	52
M18™ Vacuums	52
M18™ Jobsite Fan	52
M18™ / M12™ Jobsite Speaker	23, 53
M18™ Radios	52
M18™ Power Source	53

BATTERIES & CHARGERS

M12™ Chargers	23
M12™ Batteries	24
M18™ Chargers	53
M18™ Batteries	54

COMBO KITS

M12™ Combo Kits	25
M18™ Combo Kits	55



2017 CORDLESS CATALOG

