



SUBMITTAL SHEETS

LINE VOLTAGE LIGHTING - H


2015




Catalog#: 2033
3-TIER PAGODA LIGHT

Category Line Voltage
Page [H1](#)

Specifications:

Material	Cast Aluminum
Socket	Premium Grade Porcelain Socket with Nickel contacts and Teflon-jacketed wire leads
Gasket	Sealed with High Grade Weatherproof Silicone Gasket
Wiring	Pre-wired with 24" SPT-1 Cord
Voltage	120 Volts
Lamp type	Medium Base E26 Socket Lamp Not Included, 60W Max.
Lens type	Frosted Glass Lens - Standard, Clear lens by request
Accessories	3-Tier 8" Extension Wand
Certifications	



Cat. No.	Finishes	UPC
2033-BK	Black	615624264389
2033-BR	Bronze	615624266543
2033-GN	Green	615624264396
2033-VG	Verde Green	615624264402







Catalog#: 2037
3-TIER COMP. FLUOR. PAGODA LIGHT

Category Line Voltage
Page [H1](#)

Specifications:

Material	Cast Aluminum
Socket	Premium Grade Porcelain Socket with Nickel contacts and Teflon-jacketed wire leads
Gasket	Sealed with High Grade Weatherproof Silicone Gasket
Wiring	Pre-wired with 24" SPT-1 Cord
Voltage	120 Volts
Lamp type	PLQ9 9W Lamp Included
Lens type	Frosted Glass Lens - Standard, Clear lens by request
Accessories	3-Tier 8" Extension Wand
Certification	



Cat. No.	Finishes	UPC
2037-BK	Black	615624264419
2037-BR	Bronze	615624268882
2037-GN	Green	615624264426
2037-VG	Verde Green	615624264433





Catalog#: 2044
4-TIER PAGODA LIGHT


Category


Line Voltage

Page

[H1](#)

Specifications:

Material	Cast Aluminum
Socket	Premium Grade Porcelain Socket with Nickel contacts and Teflon-jacketed wire leads
Gasket	Sealed with High Grade Weatherproof Silicone Gasket
Wiring	Pre-wired with 24" SPT-1 Cord
Voltage	120 Volts
Lamp type	Medium Base E26 Socket Lamp Not Included, 60W Max.
Lens type	Frosted Glass Lens - Standard, Clear lens by request
Accessories	4-Tier 8" Extension Wand
Certification	



Cat. No.	Finishes	UPC
2044-BK	Black	615624264471
2044-BR	Bronze	615624267670
2044-GN	Green	615624264488
2044-VG	Verde Green	615624264495





Catalog#: 2047
4-TIER COMP. FLUOR. PAGODA LIGHT


Category


Line Voltage

Page

[H1](#)

Specifications:

Material	Cast Aluminum
Socket	Premium Grade Porcelain socket with Nickel contacts and Teflon-jacketed wire leads
Gasket	Sealed with High Grade Weatherproof Silicone Gasket
Wiring	Pre-wired with 24" SPT-1 Cord
Voltage	120 Volts
Lamp type	PLQ13 13W Lamp Included
Lens type	Frosted Glass Lens - Standard, Clear lens by request
Accessories	4-Tier 8" Extension Wand
Certification	



Cat. No.	Finishes	UPC
2047-BK	Black	615624264501
2047-BR	Bronze	615624267687
2047-GN	Green	615624264518
2047-VG	Verde Green	615624264525






Catalog#: S613
120V 1-PL13 FLOOD FIXTURE

Category Line Voltage
Page [H2](#)

Specifications:

Material Cast Aluminum
Socket Premium Grade Porcelain socket with Nickel contacts and Teflon-jacketed wire leads
Gasket Sealed with High Grade Weatherproof Silicone Gasket
Wiring Pre-wired with 24" SPT-1 Cord
Voltage 120 Volts
Lamp type PL13 Lamp Included
Lens type Tempered Glass Lens
Certification



Cat. No.	Finishes	UPC
S613-BK	Black	615624265416
S613-BR	Bronze	615624265423
S613-GN	Green	615624373784
S613-WH	White	615624000246







Catalog#: S626
120V 2-PL13 FLOOD FIXTURE

Category Line Voltage
Page [H2](#)

Specifications:

Material Cast Aluminum
Socket Premium Grade Porcelain socket with Nickel contacts and Teflon-jacketed wire leads
Gasket Sealed with High Grade Weatherproof Silicone Gasket
Wiring Pre-wired with 24" SPT-1 Cord
Voltage 120 Volts
Lamp type 2 X PL13 Lamp Included
Lens type Tempered Glass Lens
Certification 



Cat. No.	Finishes	UPC
S626-BK	Black	615624265447
S626-BR	Bronze	615624265454
S626-GN	Green	615624265775
S626-WH	White	615624265461







Catalog#: S626L
120V LONG 2-PL13 FLOOD FIXTURE

Category Line Voltage
Page [H2](#)

Specifications:

Material	Cast Aluminum
Socket	Premium Grade Porcelain socket with Nickel contacts and Teflon-jacketed wire leads
Gasket	Sealed with High Grade Weatherproof Silicone Gasket
Wiring	Pre-wired with 24" SPT-1 Cord
Voltage	120 Volts
Lamp type	2 X PL13 Lamp Included
Lens type	Tempered Glass Lens Wide Flood
Certification	



Cat. No.	Finishes	UPC
S626L-BK	Black	615624268455







Catalog#: S626S
120V 2-PL13 FLOOD FIXTURE COMPACT

Category Line Voltage
Page [H2](#)

Specifications:

Material Cast Aluminum
Socket Premium Grade Porcelain socket with Nickel contacts and Teflon-jacketed wire leads
Gasket Sealed with High Grade Weatherproof Silicone Gasket
Wiring Pre-wired with 24" SPT-1 Cord
Voltage 120 Volts
Lamp type 2 X PL13 Lamp Included
Lens type Tempered Glass Lens
Certification 



Cat. No.	Finishes	UPC
S626S-BK	Black	615624268424
S626S-BR	Bronze	615624268431
S626S-WH	White	615624268448







Catalog#: P613
120V 1-PL13 PLASTIC FIXTURE - BLACK

Category Line Voltage
Page [H3](#)

Specifications:

Material	Heavy-Duty ABS Plastic
Socket	Premium Grade Porcelain socket with Nickel contacts and Teflon-jacketed wire leads
Gasket	Sealed with High Grade Weatherproof Silicone Gasket
Wiring	Pre-wired with 24" SPT-1 Cord
Voltage	120 Volts
Lamp type	PL13 Lamp Included
Lens type	Acrylic Lens
Certification	



Cat. No.	Finishes	UPC
P613	Black	615624268462







Catalog#: P626
120V 2-PL13 PLASTIC FIXTURE - BLACK

Category Line Voltage
Page [H3](#)

Specifications:

Material	Heavy-Duty ABS Plastic
Socket	Premium Grade Porcelain socket with Nickel contacts and Teflon-jacketed wire leads
Gasket	Sealed with High Grade Weatherproof Silicone Gasket
Wiring	Pre-wired with 24" SPT-1 Cord
Voltage	120 Volts
Lamp type	2 X PL13 Lamp Included
Lens type	Acrylic Lens
Certification	



Cat. No.	Finishes	UPC
P626	Black	615624268479







Catalog#: P639
3XPL13 39W PLASTIC FLOOD FIXTURE

Category Line Voltage
Page [H3](#)

Specifications:

Material	Heavy-Duty ABS Plastic
Socket	Premium Grade Porcelain socket with Nickel contacts and Teflon-jacketed wire leads
Gasket	Sealed with High Grade Weatherproof Silicone Gasket
Wiring	Pre-wired with 24" SPT-1 Cord
Voltage	120 Volts
Lamp type	3 X PL13 Lamp Included
Lens type	Acrylic Lens
Certification	



Cat. No.	Finishes	UPC
P639	Black	615624268486







Catalog#: HL16
PAR16 BULLET 120V

Category Line Voltage
Page [H4](#)

Specifications:

Material	Cast Aluminum
Socket	Premium Grade Porcelain socket with Nickel contacts and Teflon-jacketed wire leads
Gasket	Sealed with High Grade Weatherproof Silicone Gasket
Wiring	Pre-wired with 24" SPT-1 Cord
Voltage	120 Volts
Lamp type	PAR16 or JDR16 Lamp Not Included, 50W Max.
Lens type	Tempered Glass Lens
Accessories	O-Ring Silicone Gasket
Certification	



Cat. No.	Finishes	UPC
HL16-BK	Black	615624266901
HL16-BR	Bronze	615624266918
HL16-GN	Green	615624266925
HL16-WH	White	615624266932







Catalog#: HL20
PAR20 BULLET WITH GLASS HOOD

Category Line Voltage
Page [H4](#)

Specifications:

Material	Cast Aluminum
Socket	Premium Grade Porcelain socket with Nickel contacts and Teflon-jacketed wire leads
Gasket	Sealed with High Grade Weatherproof Silicone Gasket
Wiring	Pre-wired with 24" SPT-1 Cord
Voltage	120 Volts
Lamp type	PAR20 Lamp Not Included, 50W Max.
Lens type	Tempered Glass Lens
Accessories	O-Ring Silicone Gasket
Certification	



Cat. No.	Finishes	UPC
HL20-BK	Black	615624268523
HL20-BR	Bronze	615624268530
HL20-GN	Green	615624268547
HL20-WH	White	615624268554
HL20-SA	Sand	615624373296







Catalog#: HL20S
PAR20 BULLET WITH SQUARE HOOD

Category Line Voltage
Page [H4](#)

Specifications:

Material	Cast Aluminum
Socket	Premium Grade Porcelain socket with Nickel contacts and Teflon-jacketed wire leads
Gasket	Sealed with High Grade Weatherproof Silicone Gasket
Wiring	Pre-wired with 24" SPT-1 Cord
Voltage	120 Volts
Lamp type	PAR20 Lamp Not Included, 50W Max.
Lens type	Tempered Glass Lens
Accessories	O-Ring Silicone Gasket
Certification	



Cat. No.	Finishes	UPC
HL20S-BK	Black	615624373340
HL20S-BR	Bronze	615624373357
HL20S-GN	Green	615624373364
HL20S-WH	White	615624373371







Catalog#: HL30
PAR30 BULLET WITH GLASS HOOD

Category Line Voltage
Page [H4](#)

Specifications:

Material	Cast Aluminum
Socket	Premium Grade Porcelain socket with Nickel contacts and Teflon-jacketed wire leads
Gasket	Sealed with High Grade Weatherproof Silicone Gasket
Wiring	Pre-wired with 24" SPT-1 Cord
Voltage	120 Volts
Lamp type	PAR30 Lamp Not Included, 75W Max.
Lens type	Tempered Glass Lens
Accessories	O-Ring Silicone Gasket
Certification	



Cat. No.	Finishes	UPC
HL30-BK	Black	615624268561
HL30-BR	Bronze	615624268578
HL30-GN	Green	615624268585
HL30-WH	White	615624268592







Catalog#: FGHL20
FIBER GLASS PAR20 BULLET

Category Line Voltage
Page [H5](#)

Specifications:

Material	Composite
Socket	Premium Grade Porcelain socket with Nickel contacts and Teflon-jacketed wire leads
Gasket	Sealed with High Grade Weatherproof Silicone Gasket
Wiring	Pre-wired with 24" SPT-1 Cord
Voltage	120 Volts
Lamp type	PAR20 Lamp Not Included, 50W Max.
Lens type	Convex Acrylic Lens
Accessories	O-Ring Silicone Gasket
Certification	



Cat. No.	Finishes	UPC
FGHL20	Bronze	615624272971







Catalog#: FGHL38
FIBER GLASS PAR38 BULLET

Category Line Voltage
Page [H5](#)

Specifications:

Material	Composite
Socket	Premium Grade Porcelain socket with Nickel contacts and Teflon-jacketed wire leads
Gasket	Sealed with High Grade Weatherproof Silicone Gasket
Wiring	Pre-wired with 24" SPT-1 Cord
Voltage	120 Volts
Lamp type	PAR38 Lamp Not Included, 90W Max.
Lens type	Tempered Glass Lens
Accessories	O-Ring Silicone Gasket Optional Glare Shield Available [FG38V]
Certification	



Cat. No.	Finishes	UPC
FGHL38	Bronze	615624272971





Catalog#: HL31-ARB
PAR30 bullet


Category


Line Voltage

Page

[H5](#)

Specifications:

Material	Solid Brass
Socket	Premium Grade Porcelain socket with Nickel contacts and Teflon-jacketed wire leads
Gasket	Sealed with High Grade Weatherproof Silicone Gasket
Wiring	Pre-wired with 24" SPT-1 Cord
Voltage	120 Volts
Lamp type	PAR30 Lamp Not Included, 75W Max.
Accessories	6" Stem Included
Certification	



Cat. No.	Finishes	UPC
HL31-ARB	Architectural Bronze	615624387705







Catalog#: HL31-COP
PAR30 bullet

Category Line Voltage
Page [H5](#)

Specifications:

Material	Solid Copper Polished
Socket	Premium Grade Porcelain socket with Nickel contacts and Teflon-jacketed wire leads
Gasket	Sealed with High Grade Weatherproof Silicone Gasket
Wiring	Pre-wired with 24" SPT-1 Cord
Voltage	120 Volts
Lamp type	PAR30 Lamp Not Included, 75W Max.
Accessories	6" Stem Included
Certification	



Cat. No.	Finishes	UPC
HL31-COP	Copper	615624387699







Catalog#: HL2
PAR38 BULLET - DIE CAST ALUMINUM

Category Line Voltage
Page [C13](#) / [H6](#)

Specifications:

Material	Cast Aluminum
Socket	Premium Grade Porcelain socket with Nickel contacts and Teflon-jacketed wire leads
Gasket	Sealed with High Grade Weatherproof Silicone Gasket
Wiring	Pre-wired with 24" SPT-1 Cord
Voltage	120 Volts
Lamp type	PAR38 Lamp Not Included, 90W Max.
Accessories	O-Ring Silicone Gasket
Certification	



Cat. No.	Finishes	UPC
HL2-BK	Black	835243006287
HL2-GY	Gray	835243006300
HL2-GN	Green	835243006294
HL2-WH	White	835243008441







Catalog#: HL38
PAR38 BULLET WITH GLASS HOOD

Category Line Voltage
Page [H6](#)

Specifications:

Material	Cast Aluminum
Socket	Premium Grade Porcelain socket with Nickel contacts and Teflon-jacketed wire leads
Gasket	Sealed with High Grade Weatherproof Silicone Gasket
Wiring	Pre-wired with 24" SPT-1 Cord
Voltage	120 Volts
Lamp type	PAR38 Lamp Not Included, 90W Max.
Lens type	Tempered Glass Lens
Accessories	O-Ring Silicone Gasket Optional Glare Shield [38V]
Certification	



Cat. No.	Finishes	UPC
HL38-BK	Black	615624266819
HL38-BR	Bronze	615624266826
HL38-GN	Green	615624266833
HL38-WH	White	615624266840
HL38-SA	Sand	615624373487





Catalog#: LH90
PREMIUM PAR38 LAMP HOLDER

Category Line Voltage
Page [C13](#) / [H6](#)

Specifications:

Material Cast Aluminum

Socket Premium Grade Porcelain socket with Nickel contacts and Teflon-jacketed wire leads


Gasket Sealed with High Grade Weatherproof Silicone Gasket

Wiring Pre-wired with 24" SPT-1 Cord

Voltage 120 Volts

Lamp type PAR38 Lamp Not Included, 90W Max.

Accessories Black Silicone Gasket Seals Lamp Premium Lamp Holder



Certification 

Cat. No.	Finishes	UPC
LH90-BK	Black	835243008403
LH90-GY	Gray	835243008427
LH90-BR	Bronze	835243008410
LH90-WH	White	835243008434





Catalog#: LH150-SG
W/P LAMPHOLDER WITH SEALING GASKET

Category Line Voltage
Page [C13](#) / [H6](#)

Specifications:

Material Cast Aluminum

Socket Premium Grade Porcelain socket with Nickel contacts and Teflon-jacketed wire leads


Gasket Sealed with High Grade Weatherproof Silicone Gasket

Wiring Pre-wired with 24" SPT-1 Cord

Voltage 120 Volts

Lamp type PAR38 Lamp Not Included, 90W Max.

Accessories Black Silicone Gasket Seals Lamp Premium Lamp Holder



Certification 

Cat. No.	Finishes	UPC
LH150-SG-BK	Black	835243007819
LH150-SG-GY	Gray	835243006317
LH150-SG-BR	Bronze	835243007826
LH150-SG-WH	White	835243006362







Catalog#: QH150
150W OUTDOOR QUARTZ FLOOD LIGHT

Category Line Voltage
Page [H7](#)

Specifications:

Material	Cast Aluminum
Socket	Premium Grade Porcelain socket with Nickel contacts and Teflon-jacketed wire leads
Gasket	Sealed with High Grade Weatherproof Silicone Gasket
Wiring	Pre-wired with 24" SPT-1 Cord
Voltage	120 Volts
Lamp type	Q150T3/S 150W Lamp Included
Lens type	Tempered Glass Lens
Certification	



Cat. No.	Finishes	UPC
QH150-BK	Black	615624267274
QH150-BR	Bronze	615624265881
QH150-WH	White	615624265898







Catalog#: QH300
300W OUTDOOR QUARTZ FLOOD LIGHT

Category Line Voltage
Page [H7](#)

Features:

Material Cast Aluminum
Socket Premium Grade Porcelain socket with Nickel contacts and Teflon-jacketed wire leads
Gasket Sealed with High Grade Weatherproof Silicone Gasket
Wiring Pre-wired with 24" SPT-1 Cord
Voltage 120 Volts
Lamp type Double Ended T3 300W Lamp Included
Lens type Tempered Glass Lens
Certification 



Cat. No.	Finishes	UPC
QH300-BK	Black	615624268509
QH300-BR	Bronze	615624265904
QH300-WH	White	615624265911







Catalog#: QH500
500W OUTDOOR QUARTZ FLOOD LIGHT

Category Line Voltage
Page [H7](#)

Features:

Material Cast Aluminum
Socket Premium Grade Porcelain socket with Nickel contacts and Teflon-jacketed wire leads
Gasket Sealed with High Grade Weatherproof Silicone Gasket
Wiring Pre-wired with 24" SPT-1 Cord
Voltage 120 Volts
Lamp type Double Ended T3 500W Lamp Included
Lens type Tempered Glass Lens
Certification 



Cat. No.	Finishes	UPC
QH500-BK	Black	615624267281
QH500-BR	Bronze	615624265928
QH500-WH	White	615624265935







Catalog#: QH1500
1500W OUTDOOR QUARTZ FLOOD LIGHT

Category Line Voltage
Page [H7](#)

Features:

- Material Cast Aluminum
- Socket Premium Grade Porcelain socket with Nickel contacts and Teflon-jacketed wire leads
- Gasket Sealed with High Grade Weatherproof Silicone Gasket
- Wiring Pre-wired with 24" SPT-1 Cord
- Voltage 120 Volts
- Lamp type Double Ended 1500W Lamp Included
- Lens type Tempered Glass Lens
- Accessories Optional Double Ended 1000W Lamp
- Certification 



Cat. No.	Finishes	UPC
QH1500	Bronze	615624265942







Catalog#: QH1500-240
1500W 240V QUARTZ FLOOD LIGHT

Category Line Voltage
Page [H7](#)

Features:

- Material** Cast Aluminum
- Socket** Premium Grade Porcelain socket with Nickel contacts and Teflon-jacketed wire leads
- Gasket** Sealed with High Grade Weatherproof Silicone Gasket
- Wiring** Pre-wired with 24" SPT-1 Cord
- Voltage** 240 Volts
- Lamp type** Double Ended 1500W Lamp Included
- Lens type** Tempered Glass Lens
- Certification** 



Cat. No.	Finishes	UPC
QH1500-240	Bronze	615624265959







Catalog#: QR100
100W W/P QUARTZ FLOOD LIGHT + LAMP

Category Line Voltage
Page [C13 / H7](#)

Specifications:

Material	Cast Aluminum
Socket	Premium Grade Porcelain socket with Nickel contacts and Teflon-jacketed wire leads
Gasket	Sealed with High Grade Weatherproof Silicone Gasket
Wiring	Pre-wired with 24" SPT-1 Cord
Voltage	120 Volts
Lamp type	100W T4 Lamp Included
Lens type	Tempered Glass Lens
Certification	



Cat. No.	Finishes	UPC
QR100-BK	Black	615624266031
QR100-BR	Bronze	615624266024
QR100-GY	Gray	615624266017
QR100-WH	White	615624266048






Catalog#: 5210
120V PAR38 WELL LIGHT - BLACK

Category Line Voltage
Page [H8](#)

Features:

Material Cast Aluminum
Voltage 120 Volts
Lamp type PAR38 Lamp Not Included, 75W Max.
Lens type Tempered Glass Lens
Accessories 3 Holes on the bottom: 1 SJT Cord, 1-Plug and 1-Blank 24" SJT Cord



Cat. No.	Finishes	UPC
5210	Black	615624267878






Catalog#: 5212
120V PAR38 WELL LIGHT W/ LOUVER - BLACK

Category Line Voltage
Page [H8](#)

Features:

Material Cast Aluminum
Voltage 120 Volts
Lamp type PAR38 Lamp Not Included,
75W Max.
Lens type Tempered Glass Lens
Accessories 3 Holes on the bottom: 1 SJT
Cord, 1-Plug and 1-Blank
24" SJT Cord



Cat. No.	Finishes	UPC
5212	Black	615624267885






Catalog#: 5213
120V PAR38 WELL LIGHT W/ LOUVER - BLACK

Category Line Voltage
Page [H8](#)

Features:

Material Cast Aluminum
Voltage 120 Volts
Lamp type PAR38 Lamp Not Included, 75W Max.
Lens type Tempered Glass Lens
Accessories 3 Holes on the bottom: 1 SJT Cord, 1-Plug and 1-Blank 24" SJT Cord



Cat. No.	Finishes	UPC
5213	Black	615624267892






Catalog#: 5214
120V PAR38 WELL LIGHT W/ CANOPY - BLACK

Category Line Voltage
Page [H8](#)

Features:

Material Cast Aluminum
Voltage 120 Volts
Lamp type PAR38 Lamp Not Included,
75W Max.
Lens type Tempered Glass Lens
Accessories 3 Holes on the bottom: 1 SJT
Cord, 1-Plug and 1-Blank
24" SJT Cord



Cat. No.	Finishes	UPC
5214	Black	615624267908






Catalog#: FG5210
FIBER GLASS 120V PAR38 WELL LIGHT

Category Line Voltage
Page [H8](#)

Features:

Material Fiberglass
Voltage 120 Volts
Lamp type PAR38 Lamp Not Included, 75W Max.
Lens type Tempered Glass Lens
Accessories 3 Holes on the bottom: 1 SJT Cord, 1-Plug and 1-Blank Corrosion Resistant



Cat. No.	Finishes	UPC
FG5210	Black	615624267915






Catalog#: FG5213
FIBER GLASS 120V PAR38 WELL LT W/ LOUV

Category Line Voltage
Page [H8](#)

Features:

Material Fiberglass
Voltage 120 Volts
Lamp type PAR38 Lamp Not Included, 75W Max.
Lens type Tempered Glass Lens
Accessories 3 Holes on the bottom: 1 SJT Cord, 1-Plug and 1-Blank Corrosion Resistant



Cat. No.	Finishes	UPC
FG5213	Black	615624267922






Catalog#: 5610-MH70
STAINLESS STEEL MH70 WELL LIGHT

Category Line Voltage
Page [H9](#)

Features:

- Material: Stainless Steel Construction in PVC Sleeve
- Voltage: 120/208/240/277 Quad Tap CWA
- Lamp type: Double Ended 70W Metal Halide Lamp Included
- Lens type: Heavy-Duty Tempered Glass Lens
- Accessories: Stainless Steel Screws
1 Hole on the bottom with SJT Cord



Cat. No.	Finishes	UPC
5610-MH70	Stainless Steel	615624269858






Catalog#: 5710-MH100
STAINLESS STEEL MH100 WELL LIGHT

Category Line Voltage
Page [H9](#)

Features:

Material Stainless Steel Construction in PVC Sleeve
Voltage 120/208/240/277 Quad Tap CWA
Lamp type Double Ended 100W Metal Halide Lamp Included
Lens type Heavy-Duty Tempered Glass Lens
Accessories Stainless Steel Screws
 1 Hole on the bottom with SJT Cord



Cat. No.	Finishes	UPC
5710-MH100	Stainless Steel	615624269865






Catalog#: 5711-MH100
STAINLESS STEEL MH100 WELL LIGHT

Category Line Voltage
Page [H9](#)

Features:

- Material: Stainless Steel Construction in PVC Sleeve
- Voltage: 120/208/240/277 Quad Tap CWA
- Lamp type: Double Ended 100W Metal Halide Lamp Included
- Lens type: Heavy-Duty Tempered Glass Lens
- Accessories: Stainless Steel Screws
1 Hole on the bottom with SJT Cord



Cat. No.	Finishes	UPC
5711-MH100	Stainless Steel	615624269872






Catalog#: FG5610-MH70
FIBERGLASS MH70 WELL LIGHT

Category Line Voltage
Page [H10](#)

Features:

- Material: Fiberglass
- Voltage: 120/208/240/277 Quad Tap CWA
- Lamp type: Double Ended 70W Metal Halide Lamp Included
- Lens type: Heavy-Duty Tempered Glass Lens
- Accessories: Stainless Steel Screws
 3 Holes on the bottom: 1-SJT Cord, 1-Plug and 1-Blank



Cat. No.	Finishes	UPC
FG5610-MH70	Bronze	615624272933






Catalog#: FG5612-MH70
FIBERGLASS MH70 WELL LIGHT

Category Line Voltage
Page [H10](#)

Features:

- Material: Fiberglass
- Voltage: 120/208/240/277 Quad Tap CWA
- Lamp type: Double Ended 70W Metal Halide Lamp Included
- Lens type: Heavy-Duty Tempered Glass Lens
- Accessories: Stainless Steel Screws
 3 Holes on the bottom: 1-SJT Cord, 1-Plug and 1-Blank



Cat. No.	Finishes	UPC
FG5612-MH70	Bronze	615624272940






Catalog#: FG5710-MH100
FIBERGLASS MH100 WELL LIGHT

Category Line Voltage
Page [H10](#)

Features:

Material Fiberglass
Voltage 120/208/240/277 Quad Tap CWA
Lamp type Medium Base 100W Metal Halide Lamp Included
Lens type Heavy-Duty Tempered Glass Lens
Accessories Stainless Steel Screws
 2 Holes on the bottom: 1 SJT Cord, 1-Plug and 1-Blank



Cat. No.	Finishes	UPC
FG5710-MH100	Bronze	615624272957






Catalog#: FG5712-MH100
FIBERGLASS MH100 WELL LIGHT

Category Line Voltage
Page [H10](#)

Features:

Material Fiberglass
Voltage 120/208/240/277 Quad Tap CWA
Lamp type Medium Base 100W Metal Halide Lamp Included
Lens type Heavy-Duty Tempered Glass Lens
Accessories Stainless Steel Screws
 2 Holes on the bottom: 1 SJT Cord, 1-Plug and 1-Blank



Cat. No.	Finishes	UPC
FG5712-MH100	Bronze	615624272964






Catalog#: 7210C
STEP LIGHT COVER PLATE

Category Line Voltage
Page [G38](#) / [H11](#)

Features:

- Material Cast Aluminum
- Socket Premium Grade Porcelain Socket
- Pulse Rated
- Gasket Sealed with High Grade
Weatherproof Silicone Gasket
- Wiring Pre-wired Teflon-Jacketed 9"
Pigtail
- Lens type Frosted Glass Lens
- Housing Fits with [7210H-E26](#) and
[7210H-PL9](#)



Cat. No.	Finishes	UPC
7210C-BK	Black	615624270502
7210C-BR	Bronze	615624270519
7210C-WH	White	615624270526






Catalog#: 7210H-E26
INCANDESCENT HOUSING FOR 7210 SERIES

Category Line Voltage
Page [H11](#)

Features:


Material	Powder Coated Cast Aluminum
Socket	Premium Grade Porcelain Socket
Gasket	Sealed with High Grade Weatherproof Silicone Gasket
Wiring	Pre-wired 9" 18/2 SPT-1 Cord
Lamp type	T-10 Lamp Not Included, 40W Max.
Accessories	Silicone Gasket Fits with 7210C or 7212C Coverplates

Dimensions:



Cat. No.	UPC
7210H-E26	615624270618






Catalog#: 7210H-PL9
PL9 HOUSING FOR 7210 SERIES

Category Line Voltage
Page [H11](#)

Features:


Material	Powder Coated Cast Aluminum
Socket	Premium Grade Porcelain Socket
Gasket	Sealed with High Grade Weatherproof Silicone Gasket
Wiring	Pre-wired 9" 18/2 SPT-1 Cord
Lamp type	PL9 Lamp Included
Accessories	Silicone Gasket Fits with 7210C or 7212C Coverplates

Dimensions:



Cat. No.	UPC
7210H-PL9	615624270625





Catalog#: 7212C
STEP LIGHT COVER PLATE

Category

Line Voltage

Page

[G38](#) / [H11](#)

Features:

- Material: Cast Aluminum
- Lens type: Frosted Glass Lens
- Housing: Fits [7210H-E26](#) and [7210H-PL9](#)



Cat. No.	Finishes	UPC
7212C-BK	Black	615624270540
7212C-BR	Bronze	615624270557
7212C-WH	White	615624270571






Catalog#: S710H-E26
120V 40W STEP LIGHT HOUSING

Category Line Voltage
Page [H12](#)

Features:

Material Powder Coated Cast Aluminum
Socket Premium Grade Porcelain Socket
Gasket Sealed with High Grade Weatherproof Silicone Gasket
Wiring Pre-wired 9" 18/2 SPT-1 Cord
Voltage 120 Volts
Lamp type T-10 Lamp Not Included, 40W Max.
Accessories Silicone Gasket
 Medium Base Socket
 Fits [S710C](#), [S711C](#), [S712C](#) or [S713C](#) Coverplates

Dimensions:



Cat. No.	UPC
S710H-E26	615624373821







Catalog#: S710H-LED-120V
120V LED STEP LIGHT HOUSING

Category Line Voltage
Page [H12](#) / [38](#) [39](#) [40](#) (LED Catalog)

Features:

Material	Powder Coated Cast Aluminum
Gasket	Sealed with High Grade Weatherproof Silicone Gasket
Wiring	Pre-wired 9" 18/2 SPT-1 Cord
Voltage	120 Volts
Power	5.70W Input Power
Color Temperature	4000K
Accessories	Silicone Gasket Fits with S710C , S711C or S713C Coverplates



Cat. No.	UPC
S710H-LED-120V	615624373838






Catalog#: S710H-PLQ9
PLQ9 HSNG ASMBLY FOR S710 SERIES

Category Line Voltage
Page [H12](#)

Features:

Material	Powder Coated Cast Aluminum
Socket	Premium Grade Porcelain Socket
Gasket	Sealed with High Grade Weatherproof Silicone Gasket
Wiring	Pre-wired 9" 18/2 SPT-1 Cord
Voltage	120 Volts
Lamp type	PLQ9 9W Lamp Included
Accessories	Silicone Gasket Fits with S710C , S711C or S713C Coverplates



Cat. No.	UPC
S710H-PLQ9	615624373869






Catalog#: S710H-PLQ13
PLQ13 STEP LIGHT HOUSING

Category Line Voltage
Page [H12](#)

Features:

Material Powder Coated Cast Aluminum
Voltage 120 Volts
Lamp type PLQ13 13W Lamp Included
Accessories Silicone Gasket
 Fits with [S710C](#), [S711C](#) or [S713C](#)
 Coverplates



Cat. No.	UPC
S710H-PLQ13	615624373852





Catalog#: 7711 SERIES

OUTDOOR BULKHEAD LIGHT - WHITE, OPAL POLYCARBONATE LENS

Category Line Voltage
Page [H13](#)

Features:

Material Cast Aluminum
 Silicone Gasket


Socket Premium grade Porcelain socket -
 Pulse Rated

Gasket Sealed with High Grade
 Weatherproof Silicone Gasket

Wiring Pre-wired Teflon-jacketed 9"
 Pigtail

Voltage 120 Volts

Lens type Opal Polycarbonate Lens



Cat. No.	Wattage	Lamp Type	UPC
7711-A19	100W	Medium Base E26 Socket (Not Included)	615624265690
7711-PL13	13W	1 PLQ13 (Included)	615624270847
7711-PL26	26W	2 PLQ13 (Included)	615624265706






Catalog#: 7712 SERIES

OUTDOOR BULKHEAD LIGHT - WHITE, OPAL POLYCARBONATE LENS

Category Line Voltage
Page [H13](#)

Features:

Material Cast Aluminum
 Silicone Gasket
Socket Premium grade Porcelain socket -
 Pulse Rated
Gasket Sealed with High Grade
 Weatherproof Silicone Gasket
Wiring Pre-wired Teflon-jacketed 9"
 Pigtail
Voltage 120 Volts
Lens type Opal Polycarbonate Lens



Cat. No.	Wattage	Lamp Type	UPC
7712-A19	100W	Medium Base E26 Socket (Not Included)	615624265713
7712-PL13	13W	1 PL13 (Included)	615624270854
7712-PL26	26W	2 PL13 (Included)	615624265737





Catalog#: 7910 SERIES

OUTDOOR BULKHEAD LIGHT - WHITE, FROSTED GLASS LENS

Category


Line Voltage

Page

[H13](#)

Features:

Material	Cast Aluminum Silicone Gasket
Socket	Premium grade Porcelain socket - Pulse Rated
Gasket	Sealed with High Grade Weatherproof Silicone Gasket
Wiring	Pre-wired Teflon-jacketed 9" Pigtail
Voltage	120 Volts
Lens type	Frosted Glass Lens



Cat. No.	Wattage	Lamp Type	UPC
7910-A19	60W	Medium Base E26 Socket (Not Included)	615624271035
7910-PLQ13	13W	1 PLQ13 (Included)	615624271011
7910-PLQ26	26W	2 PLQ13 (Included)	615624271028





Catalog#: 7912 SERIES

OUTDOOR BULKHEAD LIGHT - WHITE, FROSTED GLASS LENS

Category


Line Voltage

Page

[H13](#)

Features:

- Material: Cast Aluminum
Silicone Gasket
- Socket: Premium grade Porcelain socket - Pulse Rated
- Gasket: Sealed with High Grade Weatherproof Silicone Gasket
- Wiring: Pre-wired Teflon-jacketed 9" Pigtail
- Voltage: 120 Volts
- Lens type: Frosted Glass Lens



Cat. No.	Wattage	Lamp Type	UPC
7912-A19	60W	Medium Base E26 Socket (Not Included)	615624271059
7912-PLQ13	13W	1 PLQ13 (Included)	615624271042
7912-PLQ26	26W	2 PLQ13 (Included)	615624265652





Catalog#: 7812 SERIES

OUTDOOR BULKHEAD LIGHT - WHITE, OPAL POLYCARBONATE LENS

Category


Line Voltage

Page

[H14](#)

Features:

- Material: Cast Aluminum
Silicone Gasket
- Socket: Premium grade Porcelain socket - Pulse Rated
- Gasket: Sealed with High Grade Weatherproof Silicone Gasket
- Wiring: Pre-wired Teflon-jacketed 9" Pigtail
- Voltage: 120 Volts
- Lens type: Opal Polycarbonate Lens



Cat. No.	Wattage	Lamp Type	UPC
7812-A19	100W	Medium Base E26 Socket (Not Included)	615624270885
7812-PLQ13	13W	1 PLQ13 (Included)	615624270878
7812-PLQ26	26W	2 PLQ13 (Included)	615624265683





Catalog#: 7815 SERIES

OUTDOOR BULKHEAD LIGHT - WHITE, FROSTED GLASS LENS

Category


Line Voltage

Page

[H14](#)

Features:

- Material: Cast Aluminum
Silicone Gasket
- Socket: Premium grade Porcelain socket -
Pulse Rated
- Gasket: Sealed with High Grade
Weatherproof Silicone Gasket
- Wiring: Pre-wired Teflon-jacketed 9"
Pigtail
- Voltage: 120 Volts
- Lens type: Frosted Glass Lens



Cat. No.	Wattage	Lamp Type	UPC
7815-A19	100W	Medium Base E26 Socket (Not Included)	615624270915
7815-PLQ13	13W	1 PLQ13 (Included)	615624270892
7815-PLQ26	26W	2 PLQ13 (Included)	615624270908





Catalog#: 7816 SERIES

OUTDOOR BULKHEAD LIGHT - WHITE, FROSTED GLASS LENS

Category


Line Voltage

Page

[H14](#)

Features:

- Material: Cast Aluminum
Silicone Gasket
- Socket: Premium grade Porcelain socket - Pulse Rated
- Gasket: Sealed with High Grade Weatherproof Silicone Gasket
- Wiring: Pre-wired Teflon-jacketed 9" Pigtail
- Voltage: 120 Volts
- Lens type: Frosted Glass Lens



Cat. No.	Wattage	Lamp Type	UPC
7816-A19	100W	Medium Base E26 Socket (Not Included)	615624270946
7816-PLQ13	13W	1 PLQ13 (Included)	615624270922
7816-PLQ26	26W	2 PLQ13 (Included)	615624270939





Catalog#: 7817 SERIES

OUTDOOR BULKHEAD LIGHT - WHITE OR BRONZE, FROSTED GLASS LENS

Category


Line Voltage

Page

[H14](#)

Features:

- Material: Cast Aluminum
Silicone Gasket
- Socket: Premium grade Porcelain socket - Pulse Rated
- Gasket: Sealed with High Grade Weatherproof Silicone Gasket
- Wiring: Pre-wired Teflon-jacketed 9" Pigtail
- Voltage: 120 Volts
- Lens type: Frosted Glass Lens



Cat. No.	Wattage	Lamp Type	Finish	UPC
7817-A19	100W	Medium Base E26 Socket (Not Included)	Brown	615624270991
			White	615624271004
7817-PLQ13	13W	1 PLQ13 (Included)	Brown	615624270953
			White	615624270960
7817-PLQ26	26W	2 PLQ13 (Included)	Brown	615624270977
			White	615624270984





Catalog#: 7603 SERIES

OUTDOOR BULKHEAD LIGHT - WHITE, FROSTED GLASS LENS

Category


Line Voltage

Page

[H15](#)

Features:

Material	Cast Aluminum Silicone Gasket
Socket	Premium grade Porcelain socket - Pulse Rated
Gasket	Sealed with High Grade Weatherproof Silicone Gasket
Wiring	Pre-wired Teflon-jacketed 9" Pigtail
Voltage	120 Volts
Lens type	Frosted Glass Lens



Cat. No.	Wattage	Lamp Type	UPC
7603-A19	100W	Medium Base E26 Socket (Not Included)	615624270656
7603-PLQ13	13W	1 PLQ13 (Included)	615624270649





Catalog#: 7604 SERIES

OUTDOOR BULKHEAD LIGHT - WHITE, FROSTED GLASS LENS

Category


Line Voltage

Page

[H15](#)

Features:

- Material: Cast Aluminum
Silicone Gasket
- Socket: Premium grade Porcelain socket - Pulse Rated
- Gasket: Sealed with High Grade Weatherproof Silicone Gasket
- Wiring: Pre-wired Teflon-jacketed 9" Pigtail
- Voltage: 120 Volts
- Lens type: Frosted Glass Lens



Cat. No.	Wattage	Lamp Type	UPC
7604-A19	100W	Medium Base E26 Socket (Not Included)	615624270670
7604-PLQ13	13W	1 PLQ13 (Included)	615624270663






Catalog#: 7613 SERIES

OUTDOOR BULKHEAD LIGHT - WHITE, FROSTED GLASS LENS

Category Line Voltage
Page [H15](#)

Features:

- Material Cast Aluminum
Silicone Gasket
- Socket Premium grade Porcelain socket - Pulse Rated
- Gasket Sealed with High Grade Weatherproof Silicone Gasket
- Wiring Pre-wired Teflon-jacketed 9" Pigtail
- Lens type Frosted Glass Lens



Cat. No.	Wattage	Lamp Type	UPC
7613-A19	100W	Medium Base E26 Socket (Not Included)	615624270793
7613-PLQ13	13W	1 PLQ13 (Included)	615624270786





Catalog#: 7614 SERIES

OUTDOOR BULKHEAD LIGHT - WHITE, FROSTED GLASS LENS

Category


Line Voltage

Page

[H15](#)

Features:

- Material: Cast Aluminum
Silicone Gasket
- Socket: Premium grade Porcelain socket - Pulse Rated
- Gasket: Sealed with High Grade Weatherproof Silicone Gasket
- Wiring: Pre-wired Teflon-jacketed 9" Pigtail
- Voltage: 120 Volts
- Lens type: Frosted Glass Lens



Cat. No.	Wattage	Lamp Type	UPC
7614-A19	100W	Medium Base E26 Socket (Not Included)	615624270816
7614-PLQ13	13W	1 PLQ13 (Included)	615624270809





Catalog#: 7605 SERIES

OUTDOOR BULKHEAD LIGHT - WHITE, FROSTED GLASS LENS

Category


Line Voltage

Page

[H16](#)

Features:

Material	Cast Aluminum Silicone Gasket
Socket	Premium grade Porcelain socket - Pulse Rated
Gasket	Sealed with High Grade Weatherproof Silicone Gasket
Wiring	Pre-wired Teflon-jacketed 9" Pigtail
Voltage	120 Volts
Lens type	Frosted Glass Lens



Cat. No.	Wattage	Lamp Type	UPC
7605-A19	100W	Medium Base E26 Socket (Not Included)	615624270694
7605-PLQ13	13W	1 PLQ13 (Included)	615624270687





Catalog#: 7606 SERIES

OUTDOOR BULKHEAD LIGHT- BRONZE OR WHITE, OPAL POLYCARBONATE LENS

Category


Line Voltage

Page

[H16](#)

Features:

- Material: Cast Aluminum
- Socket: Premium grade Porcelain socket - Pulse Rated
- Gasket: Sealed with High Grade Weatherproof Silicone Gasket
- Wiring: Pre-wired Teflon-jacketed 9" Pigtail
- Voltage: 120 Volts
- Lens type: Opal Polycarbonate Lens
- Color: Available in Brown or White Powder Coated Finish



Cat. No.	Wattage	Lamp Type	Finish	UPC
7606-A19	60W	Medium Base E26 Socket (Not Included)	Brown	615624270724
			White	615624270731
7606-PLQ13	13W	1 PLQ13 (Included)	Brown	615624270700
			White	615624270717





Catalog#: 7607 SERIES

OUTDOOR BULKHEAD LIGHT- BRONZE OR WHITE, OPAL POLYCARBONATE LENS

Category


Line Voltage

Page

[H16](#)

Features:

- Material: Cast Aluminum
Silicone Gasket
- Socket: Premium grade Porcelain socket - Pulse Rated
- Gasket: Sealed with High Grade Weatherproof Silicone Gasket
- Wiring: Pre-wired Teflon-jacketed 9" Pigtail
- Voltage: 120 Volts
- Lens type: Opal Polycarbonate Lens



Cat. No.	Wattage	Lamp Type	Finish	UPC
7607-A19	60W	Medium Base E26 Socket (Not Included)	Brown	615624270762
			White	615624270779
7607-PLQ13	13W	1 PLQ13 (Included)	Brown	615624270748
			White	615624270755





Catalog#: 7615 SERIES

OUTDOOR BULKHEAD LIGHT - WHITE, FROSTED GLASS LENS

Category


Line Voltage

Page

[H16](#)

Features:

Material	Cast Aluminum Silicone Gasket
Socket	Premium grade Porcelain socket - Pulse Rated
Gasket	Sealed with High Grade Weatherproof Silicone Gasket
Wiring	Pre-wired Teflon-jacketed 9" Pigtail
Voltage	120 Volts
Lens type	Frosted Glass Lens



Cat. No.	Wattage	Lamp Type	UPC
7615-A19	100W	Medium Base E26 Socket (Not Included)	615624270830
7615-PLQ13	13W	1 PLQ13 (Included)	615624270823





Catalog#: VG20-CL
REPLACEMENT GLASS FOR VPB2

Category HID LIGHTING
Page [H17](#)
Barcode

Description:

Replacement glass for Vapor-Proof Fixtures (VPB2)

Packaging Info:

Std Pkg 1
Weight

Documents:





Catalog#: VG30-CL
REPLACEMENT GLASS FOR VPB3

Category HID LIGHTING
Page [H17](#)
Barcode

Description:

Replacement glass for Vapor-Proof Fixtures (VPB3)

Packaging Info:

Std Pkg 1
Weight

Documents:






Catalog#: VPB2
150W VAPOR PROOF FIXTURE - CEILING MOUNT

Category Line Voltage
Page [H17](#)

Features:

- Material Die Cast Aluminum with Die Cast Guard
- Socket Premium grade Porcelain socket - Pulse Rated
- Gasket Sealed with High Grade Weatherproof Silicone Gasket
- Wiring Pre-wired Teflon-jacketed 9" Pigtail
- Lamp type Medium Base E26 Socket Lamp Not Included, 150W Max.
- Accessories Silicone Gasket
1/2" NPS Hub Size
Clear Glass Jar



Cat. No.	Finishes	UPC
VPB2	Clear	615624374347





Catalog#: VPB3
300W VAPOR PROOF FIXTURE - CEILING MOUNT

Category


Line Voltage

Page

[H17](#)

Features:

- Material: Die Cast Aluminum with Die Cast Guard
- Socket: Premium grade Porcelain socket - Pulse Rated
- Gasket: Sealed with High Grade Weatherproof Silicone Gasket
- Wiring: Pre-wired Teflon-jacketed 9" Pigtail
- Lamp type: Medium Base E26 Socket Lamp Not Included, 300W Max.
- Accessories: Silicone Gasket
1/2" NPS Hub Size
Clear Glass Jar



Cat. No.	Finishes	UPC
VPB3	Clear	615624374354






Catalog#: VPP2
150W VAPOR PROOF FIXTURE - PENDANT MOUNT

Category Line Voltage
Page [H17](#)

Features:

- Material Die Cast Aluminum with Die Cast Guard
- Socket Premium grade Porcelain socket - Pulse Rated
- Gasket Sealed with High Grade Weatherproof Silicone Gasket
- Wiring Pre-wired Teflon-jacketed 9" Pigtail
- Lamp type Medium Base E26 Socket Lamp Not Included, 150W Max.
- Accessories Silicone Gasket
1/2" NPS Hub Size
Clear Glass Jar



Cat. No.	Finishes	UPC
VPP2	Clear	615624374361






Catalog#: VPP3
300W VAPOR PROOF FIXTURE - PENDANT MOUNT

Category Line Voltage
Page [H17](#)

Features:

Material Die Cast Aluminum with Die Cast Guard
Socket Premium grade Porcelain socket - Pulse Rated
Gasket Sealed with High Grade Weatherproof Silicone Gasket
Wiring Pre-wired Teflon-jacketed 9" Pigtail
Lamp type Medium Base E26 Socket Lamp Not Included, 300W Max.
Accessories Silicone Gasket
 1/2" NPS Hub Size
 Clear Glass Jar



Cat. No.	Finishes	UPC
VPP3	Clear	615624374378






Catalog#: VPW2
150W VAPOR PROOF FIXTURE - WALL MOUNT

Category Line Voltage
Page [H17](#)

Features:

- Material Die Cast Aluminum with Die Cast Guard
- Socket Premium grade Porcelain socket - Pulse Rated
- Gasket Sealed with High Grade Weatherproof Silicone Gasket
- Wiring Pre-wired Teflon-jacketed 9" Pigtail
- Lamp type Medium Base E26 Socket Lamp Not Included, 150W Max.
- Accessories Silicone Gasket
1/2" NPS Hub Size
Clear Glass Jar



Cat. No.	Finishes	UPC
VPW2	Clear	615624374385





Catalog#: VPW3
300W VAPOR PROOF FIXTURE - WALL MOUNT

Category


Line Voltage

Page

[H17](#)

Features:

- Material Die Cast Aluminum with Die Cast Guard
- Socket Premium grade Porcelain socket - Pulse Rated
- Gasket Sealed with High Grade Weatherproof Silicone Gasket
- Wiring Pre-wired Teflon-jacketed 9" Pigtail
- Lamp type Medium Base E26 Socket Lamp Not Included, 300W Max.
- Accessories Silicone Gasket
1/2" NPS Hub Size
Clear Glass Jar



Cat. No.	Finishes	UPC
VPW3	Clear	615624374392





Catalog#: 8300
40" COMPLETE BOLLARD WITH A19 SOCKET, NO-LAMP

Category


Line Voltage

Page

[H18](#)

Features:

- Material: Cast Aluminum
- Voltage: 120 Volts
- Lamp type: - Medium Base E26 Socket Lamp
Not Included
- Lens type: Opal Polycarbonate Lens
- HID Ready - Select a [Conversion Kit](#)
- Includes Mounting Hardware and Anchors



Cat. No.	Finishes	UPC
8300-BK	Black	615624268349
8300-BR	Bronze	615624271080





Catalog#: 8402
32" COMPLETE BOLLARD MEDIUM BASE SOCKET, NO-LAMP

Category


Line Voltage

Page

[H18](#)

Features:

- Material: Cast Aluminum
- Voltage: 120 Volts
- Lamp type: - Medium Base E26 Socket Lamp
Not Included
- Lens type: Opal Polycarbonate Lens
- HID Ready - Select a [Conversion Kit](#)
- Includes Mounting Hardware and Anchors



Cat. No.	Finishes	UPC
8402-BK	Black	615624271196
8402-BR	Bronze	615624271202





**Catalog#: BOLLARD CONVERSION KITS
 METAL HALIDE & COMPACT FLUORESCENT CONVERSION KITS**

Category Line Voltage
Page [H18](#)

Description:

- These kits are self-contained with all necessary components including lamp and socket.
- Select a kit to convert any of the Bollards [[8300](#), [8402](#), [8330](#), [8340](#)] in minutes; Slips easily into the fixture.
- Lamp included in all kits

Cat. No.	Lamp	Ballast	Wattage
8300-MH70-KIT	Metal Halide	120/208/240/277V Quad Tap CWA	70W
8300-MH100-KIT	Metal Halide	120/208/240/277V Quad Tap CWA	100W
8300-PL26-KIT	2 X PL13	120V Input Magnetic Ballast	26W
8300-PL26E-KIT	PLQ26	120V Input Electronic Ballast	26W
8300-PL42-KIT	PLQ42	120V Input Electronic Ballast	42W





Catalog#: 8330
32" BOLLARD WITH SOCKET NO LAMP

Category


Line Voltage

Page

[H19](#)

Features:

- Material: Heavy-Duty Cast Aluminum
- Lamp type: Medium Base E26 Socket Lamp
Not Included
- Accessories: 6 levels of Tempered Glass
Includes Mounting Hardware and Anchors
Optional [Conversion Kit](#) Available



Cat. No.	Finishes	UPC
8330-BK	Black	615624271158
8330-BR	Bronze	615624271165





Catalog#: 8340
40" SPEC-GRADE BOLLARD WITH SOCKET NO-LAMP

Category


Line Voltage

Page

[H19](#)

Features:

- Material: Heavy-Duty Cast Aluminum
- Lamp type: Medium Base E26 Socket Lamp
Not Included
- Accessories: 6 levels of Tempered Glass
Includes Mounting Hardware and Anchors
Optional [Conversion Kit](#) Available



Cat. No.	Finishes	UPC
8340-BK	Black	615624271172
8340-BR	Bronze	615624271189





**Catalog#: P740 SERIES
 PLASTIC WALLPACK**

Category Line Voltage
Page [H20](#)

Features:

Material Cast Aluminum Back Plate
 ABS Housing
Socket Premium grade Porcelain socket -
 Pulse Rated
Gasket Sealed with High Grade
 Weatherproof Silicone Gasket
Wiring Pre-wired Teflon-jacketed 9"
 Pigtail
Voltage 120 Volts
Lens type Acrylic Lens
 Integrated Photocell
 Reactor Ballast



Cat. No.	Lamp	Wattage	Finish	UPC
P740-HPS70	High-Pressure Sodium	70W	Brown	615624268608
			White	615624268615
P740-PL26	2 X PL13	26W	Brown	615624268622
			White	615624268639






Catalog#: HWP7-PL84
EURO WALL PACK W/ POLY PL84 120V

Category Line Voltage
Page [H21](#)

Features:

- Die-Cast Aluminum Back Housing
- Textured Bronze Finish
- Premium grade Porcelain socket - Pulse Rated
- Sealed with High Grade Weatherproof Silicone Gasket
- Pre-wired Teflon-jacketed 9" Pigtail
- Vandal-Resistant Color-Matched Polycarbonate Front Housing
- Clear Polycarbonate Ribbed Lens
- Aluminum Reflector
- Hinged Front Housing for Easy Relamping
- Euro-Style Fluorescent Wall Pack
- Suitable for Wet Locations



Specifications:

Ballast 120~277V Electronic Ballast
 Lamp type 2 X PL42 (4-Pin, GX24Q-4 Socket) 42W, Lamp Included
 3000 lm, 82 CRI Color Rendition



Cat. No.	UPC
HWP12-MH175-PS	615624375702





**Catalog#: HWP12 SERIES
SEMI-CUTOFF WALPACK**

Category


Line Voltage

Page

[H21](#)

Features:

- Cast Aluminum Housing
- Borosilicate Molded Glass Lens
- Premium grade Porcelain socket - Pulse Rated
- Sealed with High Grade Weatherproof Silicone Gasket
- Pre-wired Teflon-jacketed 9" Pigtail
- Powder Coated Textured Bronze Finish
- Hinged Front Housing for Easy Relamping
- Medium-Base Socket 1/2 in. NPS Tapped Back Two Sides for Conduit Entrance
- Semi-Cutoff Design
- Lamp Included in all models
- Suitable for Wet Locations
- Pulse Start on Select Models
- Optional Wire Guard Available [\[WG-12\]](#)



Cat. No.	Lamp	Lumens	CRI	Wattage	Ballast	UPC
HWP12-HPS150	High-Pressure Sodium	16000 lm	22	150W	120V Reactor Ballast NPF	615624375542
HWP12-MH175-PS	Metal Halide	11700 lm	65	175W	120/208/240/277V Quad Tap CWA	615624376396





Catalog#: WG-12
WIRE GUARD FOR HWP12

Category

Line Voltage

Page

[H21](#)

Features:

Optional wire guard for [HWP12](#)

Specifications:

Material

Stainless Steel

Cat. No.	UPC
WG-12	615624375771





Catalog#: FCS-2
FULL-CUT-OFF SHROUD FOR HWP2

Category Line Voltage
Page [H22](#)

Description:

Optional Full Cutoff Shroud for [HWP2](#)

Specifications:

Material Stamped Aluminum

Cat. No.	UPC
FCS-2	615624374989





Catalog#: HWP1 SERIES
MINI WALLPACK HWP1 SERIES

Category


Line Voltage

Page

[H22](#)

Features:

- Cast Aluminum Housing
- Clear Polycarbonate Lens w/ Gasket & UV Inhibitors to Protect from Yellowing (PL42 & HPS70 Only)
- Borosilicate Molded Glass Lens (MH100 Only)
- Premium grade Porcelain Socket- Pulse Rated
- Sealed with High Grade Weatherproof Silicone Gasket
- Pre-wired Teflon-jacketed 9" Pigtail
- Powder Coated Textured Bronze Finish
- Fluorescent Socket and Bracket for 42W PL Model
- 1/2 in. NPS Tapped Back and Sides for Conduit Entrance
- Medium Base E26 Socket for HPS & MH Model
- Lamp Included in all models
- Suitable for Wet Locations



Cat. No.	Lamp	Lumens	CRI	Wattage	Ballast	UPC
HWP1-HPS70	High-Pressure Sodium	28000 lm	22	70W	NPF	615624374927
HWP1-MH100	Metal Halide	19100 lm	65	100W	Quad Tap CWA	615624375351
HWP1-PL42	PL42	51000 lm	22	42W	Electronic Ballast	615624374934





Catalog#: HWP2 SERIES
SMALL WALLPACK HWP2 SERIES

Category


Line Voltage

Page

[H22](#)

Features:

- Borosilicate Molded Glass Lens
- Cast Aluminum Housing
- Premium grade Porcelain Socket-
- Pulse Rated
- Sealed with High Grade Weatherproof Silicone Gasket
- Pre-wired Teflon-jacketed 9" Pigtail
- Powder Coated Textured Bronze Finish
- Medium Base E26 Socket
- 1/2 in. NPS Tapped Back and Sides for Conduit Entrance
- Lamp Included in both models
- Suitable for Wet Locations
- Pulse Start in Select Models
- Optional Cutoff Shroud [[FCS-2](#)] and Wire Guard Available [[WG-2](#)]



Cat. No.	Lamp	Lumens	CRI	Wattage	Ballast	UPC
HWP2-HPS150	High-Pressure Sodium	16000 lm	22	150W	120V NPF	615624374941
HWP2-MH150-PS	Metal Halide	11700 lm	65	150W	120/208/240/277V Quad Tap CWA	615624388115





Catalog#: WG-2
WIRE GUARD FOR HWP2

Category

Line Voltage

Page

[H22](#)

Description:

Optional Wire Gaurd for [HWP2](#)

Specifications:

Material

Stainless Steel

Cat. No.	UPC
WG-2	615624374972





Catalog#: FCS-4
FULL-CUT-OFF SHROUD FOR HWP3

Category

Line Voltage

Page

[H23](#)

Description:

Optional Full Cut Shroud for [HWP5](#) or [HWP4](#)

Specifications:

Material

Stamped Steel

Cat. No.	UPC
FCS-4	615624375016







**Catalog#: HWP4 SERIES
 MEDIUM WALLPACK**

Category Line Voltage
Page [H23](#)

Features:

- Cast Aluminum Housing
- Borosilicate Molded Glass Lens
- Premium Grade Porcelain Socket - Pulse Rated
- Sealed with High Grade Weatherproof Silicone Gasket
- Pre-wired Teflon-jacketed 9" Pigtail
- Powder Coated Textured Bronze Finish
- Mogul Base Socket
- 1/2 in. NPS Tapped Back and Two Sides for Conduit Entrance
- Lamp Included in both models
- Optional Full Cut Shroud [[FCS-4](#)] and Wire Guard [[WG-4](#)] Available
- Suitable for Wet Locations
- Pulse Start in Select Models



Cat. No.	Lamp	Lumens	CRI	Wattage	Ballast	UPC
HWP4-HPS250	High-Pressure Sodium	28000 lm	22	250W	120/208/240/277V Quad Tap CWA	615624374996
HWP4-MH250-PS	Metal Halide	19100 lm	65	250W	120/208/240/277V Quad Tap CWA	615624376440







**Catalog#: HWP5 SERIES
 LARGE WALLPACK**

Category Line Voltage
Page [H23](#)

Features:

- Cast Aluminum Housing
- Borosilicate Molded Glass Lens
- Premium Grade Porcelain Socket - Pulse Rated
- Sealed with High Grade Weatherproof Silicone Gasket
- Pre-wired Teflon-jacketed 9" Pigtail
- Powder Coated Textured Bronze Finish
- Mogul Base Socket
- 1/2 in. NPS Tapped Back and Two Sides for Conduit Entrance
- Lamp Included in both models
- Optional Full Cut Shroud [[FCS-4](#)] or Wire Guard [[WG-4](#)] Available
- Suitable for Wet Locations
- Pulse Start in Select Models



Cat. No.	Lamp	Lumens	CRI	Wattage	Ballast	UPC
HWP5-HPS400	High-Pressure Sodium	51000 lm	22	400W	120/208/240/277V Quad Tap CWA	615624375030
HWP5-MH400-PS	Metal Halide	33100 lm	65	400W	120/208/240/277V Quad Tap CWA	615624376457





Catalog#: WG-4
WIRE GUARD FOR HWP5 and HWP4

Category

Line Voltage

Page

[H23](#)

Description:

Optional Wire Guard for [HWP5](#) or [HWP4](#)

Specifications:

Material

Stainless Steel

Cat. No.	UPC
WG-4	615624375023





**Catalog#: HWP8 SERIES
SEMI-CUTOFF WALLPACK**

Category


Line Voltage

Page

[H24](#)

Features:

- Pulse Start on Select Models
- Cast Aluminum Housing
- Premium Grade Porcelain Socket-Pulse Rated
- Sealed with High Grade Weatherproof Silicone Gasket
- Pre-wired Teflon-jacketed 9" Pigtail
- Semi-Cutoff Design
- Tempered Clear Glass Lens
- Powder Coated Textured Bronze Finish
- Hinged Front Housing for Easy Relamping
- Medium Base E26 Socket for 150W and 175W Models
- Mogul Based Socket for 250W and 400W Models
- 1/2 in. NPS Tapped Back and Sides for Conduit Entrance
- Lamp Included in all models
- Suitable for Wet Locations



Cat. No.	Lamp	Lumens	CRI	Wattage	Ballast	UPC
HWP8-MH175	Metal Halide	11700 lm	65	175W	120/208/240/277V Quad Tap CWA	615624375726
HWP8-MH175-PS						615624376402





**Catalog#: HWP8D SERIES
SEMI-CUTOFF WALL PACK**

Category


Line Voltage

Page

[H24](#)

Features:

- Pulse Start on Select Models
- Cast Aluminum Housing
- Semi-Cutoff Design
- Tempered Clear Glass Lens
- Premium Grade Porcelain Socket-Pulse Rated
- Sealed with High Grade Weatherproof Silicone Gasket
- Pre-wired Teflon-jacketed 9" Pigtail
- Powder Coated Textured Bronze Finish
- Hinged Front Housing for Easy Relamping
- Medium Base E26 Socket for 150W and 175W Models
- Mogul Based Socket for 250W and 400W Models
- 1/2 in. NPS Tapped Back and Sides for Conduit Entrance
- Lamp Included in all models
- Suitable for Wet Locations



Cat. No.	Lamp	Lumens	CRI	Wattage	Ballast	UPC
HWP8D-HPS400	High Pressure Sodium	51000 lm	22	400W	120/208/240/277V Quad Tap CWA	615624375733
HWP8D-MH400-PS	Metal Halide	33100 lm	65			615624387286






**Catalog#: HWP8W SERIES
 SEMI-CUTOFF WALL PACK**

Category Line Voltage
Page [H24](#)

Features:

- Pulse Start on Select Models
- Cast Aluminum Housing
- Semi-Cutoff Design
- Tempered Clear Glass Lens
- Powder Coated Textured Bronze Finish
- Premium Grade Porcelain Socket-Pulse Rated
- Sealed with High Grade Weatherproof Silicone Gasket
- Pre-wired Teflon-jacketed 9" Pigtail
- Hinged Front Housing for Easy Relamping
- Medium Base E26 Socket for 150W and 175W Models
- Mogul Based Socket for 250W and 400W Models
- 1/2 in. NPS Tapped Back and Sides for Conduit Entrance
- Lamp Included in all models
- Suitable for Wet Locations



Cat. No.	Lamp	Lumens	CRI	Wattage	Ballast	UPC
HWP8W-MH250	Metal Halide	19100 lm	65	250W	120/208/240/277V Quad Tap CWA	615624375764
HWP8W-MH250-PS						615624387279





Catalog#: HWP3 SERIES
PREMIUM WALLPACK HWP3 SERIES

Category



Line Voltage

Page

[H25](#)

Features:

- Pulse Start on Select Models
- Cast Aluminum Housing
- Tempered Clear Glass Lens
- Premium Grade Porcelain Socket-Pulse Rated
- Sealed with High Grade Weatherproof Silicone Gasket
- Pre-wired Teflon-jacketed 9" Pigtail
- Powder Coated Textured Bronze Finish
- Mogul Base Socket for 250W and 400 Models
- 1/2 in. NPS Tapped Back and Sides for Conduit Entrance
- Lamp included in all models
- Suitable for Wet Locations



Cat. No.	Lamp	Lumens	CRI	Wattage	Ballast	UPC
HWP3-HPS150	High-Pressure Sodium	28000 lm	22	250W	120/208/240/277V Quad Tap CWA	615624375658
HWP3-MH175-PS	Metal Halide	11700 lm	65	175W		615624376464





**Catalog#: HWP3D SERIES
 PREMIUM WALL PACK**

Category



Line Voltage

Page

[H25](#)

Features:

- Pulse Start On Select Models
- Cast Aluminum Housing
- Tempered Clear Glass Lens
- Premium Grade Porcelain Socket-Pulse Rated
- Sealed with High Grade Weatherproof Silicone Gasket
- Pre-wired Teflon-jacketed 9" Pigtail
- Powder Coated Textured Bronze Finish
- Mogul Base Socket for 250W and 400 Models
- 1/2 in. NPS Tapped Back and Sides for Conduit Entrance
- Lamp included in all models
- Suitable for Wet Locations



Cat. No.	Lamp	Lumens	CRI	Wattage	Ballast	UPC
HWP3D-MH400-PS	Metal Halide	33100	65	400W	120/208/240/277V Quad Tap CWA	615624387309
HWP3D-MH400						615624375672





**Catalog#: HWP3W SERIES
 PREMIUM WALL PACK**

Category



Line Voltage

Page

[H25](#)

Features:

- Pulse Start On Select Models
- Cast Aluminum Housing
- Tempered Clear Glass Lens
- Premium Grade Porcelain Socket-Pulse Rated
- Sealed with High Grade Weatherproof Silicone Gasket
- Pre-wired Teflon-jacketed 9" Pigtail
- Powder Coated Textured Bronze Finish
- Mogul Base Socket for 250W and 400 Models
- 1/2 in. NPS Tapped Back and Sides for Conduit Entrance
- Lamp included in all models
- Suitable for Wet Locations



Cat. No.	Lamp	Lumens	CRI	Wattage	Ballast	UPC
HWP3W-MH250-PS	Metal Halide	19100 lm	65	250W	120/208/240/277V Quad Tap CWA	615624387293
HWP3W-MH250						615624375696





**Catalog#: HWP13 SERIES
 FULL- CUTOFF WALLPACK**

Category


Line Voltage

Page

[H26](#)

Features:

- Pulse Start on Select Models
- Cast Aluminum Housing
- Tempered Clear Glass Lens
- Premium Grade Porcelain Socket-Pulse Rated
- Sealed with High Grade Weatherproof Silicone Gasket
- Pre-wired Teflon-jacketed 9" Pigtail
- Powder Coated Textured Bronze Finish
- Medium-Base Socket
- 1/2 in. NPS Tapped Back and Sides for Conduit Entrance
- Lamp included in both models
- Suitable for Wet Locations



Cat. No.	Lamp	Lumens	CRI	Wattage	Ballast	UPC
HWP13-MH175	Metal Halide	11700 lm	65	175W	120/208/240/277V Quad Tap CWA	615624375566
HWP13-MH175-PS						615624376419






**Catalog#: HWP15 SERIES
 FULL- CUTOFF WALLPACK**

Category Line Voltage
Page [H26](#)

Features:

- Pulse Start on Select Models
- Cast Aluminum Housing
- Quarter Sphere Wall Sconce
- Tempered Clear Glass Lens
- Premium Grade Porcelain Socket-Pulse Rated
- Sealed with High Grade Weatherproof Silicone Gasket
- Pre-wired Teflon-jacketed 9" Pigtail
- Powder Coated Textured Bronze Finish
- Medium-Base E26 Socket for MH Models
- 1/2 in. NPS Tapped Back and Sides for Conduit Entrance
- Lamp Included in all models
- Suitable for Wet Locations



Cat. No.	Lamp	Lumens	CRI	Wattage	Ballast	UPC
HWP15-MH175-PS	Metal Halide	11700 lm	65	175W	120/208/240/277V Quad Tap CWA	615624387316
HWP15-PL84	2 X PL42	6000 lm	82	42W	120~277V Electronic Ballast	615624375641






**Catalog#: HWP11 SERIES
 ROUND WALLPACK**

Category
Page

Line Voltage
[H27](#)

Features:

- Pulse Start on Select Models
 - Cast Aluminum Housing
 - Quarter Sphere Wall Sconce
 - Tempered Clear Glass Lens
 - Premium Grade Porcelain Socket-Pulse Rated
 - Sealed with High Grade Weatherproof Silicone Gasket
 - Pre-wired Teflon-jacketed 9" Pigtail
 - Powder Coated Textured Bronze Finish
 - Medium-Base E26 Socket for HPS and MH models
 - 1/2 in. NPS Tapped Back and Sides for Conduit Entrance
 - Lamp included in all models
 - Suitable for Wet Locations
- Available colors in Black, Bronze, and White Powder Coated Finishes



Cat. No.	Lamp	Wattage
HWP11-HPS150	High-Pressure Sodium	150W
HWP11-MH175-PS	Metal Halide	175W
HWP11-MH175	Metal Halide	175W
HWP11-PL42	PL42	42W





Catalog#: HWP11U SERIES
ROUND WALLPACK HWPU11 SERIES

Category

Line Voltage


Page

[H27](#)

Features:

- Pulse Start on Select Models
- Cast Aluminum Housing
- Quarter Sphere Wall Sconce
- Tempered Clear Glass Lens
- Premium Grade Porcelain Socket-Pulse Rated
- Sealed with High Grade Weatherproof Silicone Gasket
- Pre-wired Teflon-jacketed 9" Pigtail
- Powder Coated Textured Bronze Finish
- Medium Base E26 Socket for HPS & MH models
- 1/2 in. NPS Tapped Back and Sides for Conduit Entrance
- Lamp Included in All models
- Suitable for Wet Locations

- Available colors in Black, Bronze, or White Powder Coated Finish



Cat. No.	Lamp	Wattage
HWP11U-HPS150	High-Pressure Sodium	150W
HWP11U-MH175-PS	Metal Halide	175W
HWP11U-MH175	Metal Halide	175W
HWP11U-PL42	PL42	42W





**Catalog#: HWP6 SERIES
 SLIM WALL PACK**

Category


Line Voltage

Page

[H28](#)

Features:

- Cast Aluminum Housing
- Slim line Wall Pack
- Borosilicate Molded Glass Lens
- Premium Grade Porcelain Socket-
- Pulse Rated
- Sealed with High Grade Weatherproof Silicone Gasket
- Pre-wired Teflon-jacketed 9" Pigtail
- Powder Coated Textured Bronze Finish
- Mogul-Base Socket
- 1/2 in. NPS Tapped Back and Sides for Conduit Entrance
- Lamp Included in all models
- Optional Wire Guard [[WG-6](#)] Available
- Suitable for Wet Locations
- Pulse Start on Select Models



Cat. No.	Lamp	Lumens	CRI	Wattage	Ballast	UPC
HWP6-HPS400	High-Pressure Sodium	51000 lm	22	400W	120/208/240/277V Quad Tap CWA	615624269346
HWP6-MH400	Metal Halide	33100 lm	65	400W	120/208/240/277V Quad Tap CWA	615624269353
HWP6-MH400-PS	Metal Halide	33100 lm	65	400W	120/208/240/277V Quad Tap CWA	615624376426






Catalog#: HWP14-MH175
ADJUSTABLE AREA/WALL PACK HPS175

Category Line Voltage
Page [H28](#)

Features:

- Cast Aluminum Housing
- Dual Purpose Adjustable Area Light/Wall Pack
- Adjustable Angle from 0° to 30°
- Tempered Clear Glass Lens
- Premium Grade Porcelain Socket-Pulse Rated
- Sealed with High Grade Weatherproof Silicone Gasket
- Pre-wired Teflon-jacketed 9" Pigtail
- Powder Coated Textured Bronze Finish
- Hinged Front Housing for Easy Relamping
- Medium-Base E26 Socket
- 1/2 in. NPS Tapped Back and Sides for Conduit Entrance
- Lamp Included
- Suitable for Wet Locations



Specifications:

Ballast 120/208/240/277V
 Quad Tap CWA
 Lamp type Metal Halide (MH) 175W,
 11700 lm, 65 CRI Color Rendition

Cat. No.	UPC
HWP14-MH175	615624375603





Catalog#: WG-6
WIRE GUARD FOR HWP6

Category Line Voltage
Page [H28](#)

Features:

Optional Wire Guard for [HWP6](#)

Specifications:

Material Stainless Steel

Cat. No.	UPC
WG-6	615625000863





Catalog#: HFL1 SERIES
HID FLOODLIGHTS FOR HFL1 SERIES

Category


Line Voltage

Page

[H29](#)

Features:

- Cast Aluminum Housing
- Tempered Clear Glass Lens
- Premium Grade Porcelain Socket - Pulse Rated
- Sealed with High Grade Weatherproof Silicone Gasket
- Pre-wired Teflon-Jacketed 9" Pigtail
- Powder Coated Textured Bronze Finish
- Hinged Front Housing for Easy Relamping
- Medium-Base E26 Socket for HPS and MH Models
- Adjustable Knuckle
- Lamp Included in all models
- Suitable for Wet Locations



Cat. No.	Lamp	Lumens	CRI	Wattage	Ballast	UPC
HFL1-HPS70	High-Pressure Sodium	6400 lm	22	70W	120V NPF	615624375078
HFL1-HPS150	High-Pressure Sodium	16000 lm	22	150W	120V NPF	615624375085
HFL1-MH70	Metal Halide	5040 lm	35	70W	120/208/240/277V Quad Tap, HX-HPF	615624375092
HFL1-PL42	PL42	3000 lm	82	42W	120-277V Electronic Ballast	615624373081






Catalog#: HFL2 SERIES
HID FLOODLIGHTS FOR HFL2 SERIES

Category Line Voltage
Page [H29](#)

Features:

- Pulse Start (PS) On Select Models
- Cast Aluminum Housing
- Tempered Clear Glass Lens
- Premium Grade Porcelain Socket - Pulse Rated
- Sealed with High Grade Weatherproof Silicone Gasket
- Pre-wired Teflon-Jacketed 9" Pigtail
- Powder Coated Textured Bronze Finish
- Hinged Front Housing for Easy Relamping
- Medium-Base E26 Socket
- Adjustable Knuckle
- Lamp Included in all models
- Standard Reflector
- Suitable for Wet Locations



Cat. No.	Lamp	Lumens	CRI	Wattage	Ballast	UPC
HFL2-MH175-PS	Metal Halide	11700 lm	65	175W	120/208/240/277V Quad Tap CWA	615624376280
HFL2S-MH175-PS	Metal Halide	11700 lm	65	175W	120/208/240/277V Quad Tap CWA	615624376297
HFL2S-MH175	Metal Halide	11700 lm	65	175W	120/208/240/277V Quad Tap CWA	615624375122





Catalog#: HFL3-MH150-PS

**HID FLOOD LIGHT METAL HALIDE 150W 120~277V
 PULSE START**

Category


Line Voltage

Page

[H30](#)

Features:

- Pulse Start
- Cast Aluminum Housing
- Tempered Clear Glass Lens
- Premium Grade Porcelain Socket - Pulse Rated
- Sealed with High Grade Weatherproof Silicone Gasket
- Pre-wired Teflon-jacketed 9" Pigtail
- Powder Coated Textured Bronze Finish
- Hinged Front Housing for Easy Relamping
- Medium-Base E26 Socket
- Round Back
- Adjustable Knuckle
- Lamp Included
- Suitable for Wet Locations



Specifications:

Ballast 120/208/240/277V
 Quad Tap CWA

Lamp type Metal Halide (MH) 150W,
 11700 lm, 65 CRI Color Rendition

Cat. No.	UPC
HFL3-MH150-PS	615624388122





Catalog#: HFL4 SERIES
SHOE BOX FLOODLIGHT HFL4 SERIES

Category


Line Voltage

Page

[H30](#)

Features:

- Pulse Start (PS) on Select Models
- Cast Aluminum Housing
- Tempered Clear Glass Lens
- Premium Grade Porcelain Socket-Pulse Rated
- Sealed with High Grade Weatherproof Silicone Gasket
- Pre-wired Teflon-jacketed 9" Pigtail
- Powder Coated Textured Bronze Finish
- Hinged Front Housing for Easy Relamping
- Mogul-Base Socket
- Mounting Yoke
- Lamp Included in all models
- Suitable for Wet Locations



Cat. No.	Lamp	Lumens	CRI	Wattage	Ballast	UPC
HFL4-HPS250	High-Pressure Sodium	28000 lm	22	250W	120/208/240/277V Quad Tap CWA	615624375139
HFL4-HPS400	High-Pressure Sodium	51000 lm	22	400W	120/208/240/277V Quad Tap CWA	615624375146
HFL4-MH250-PS	Metal Halide	19100 lm	65	250W	120/208/240/277V Quad Tap CWA	615624376310
HFL4-MH400-PS	Metal Halide	33100 lm	65	400W	120/208/240/277V Quad Tap CWA	615624376327





Catalog#: HFL5 SERIES
HID FLOODLIGHT FOR HFL5 SERIES

Category


Line Voltage

Page

[H31](#)

Features:

- Pulse Start (PS) on Select Models
- Cast Aluminum Housing
- Tempered Clear Glass Lens
- Premium Grade Porcelain Socket-Pulse Rated
- Sealed with High Grade Weatherproof Silicone Gasket
- Pre-wired Teflon-jacketed 9" Pigtail
- Powder Coated Textured Bronze Finish
- Hinged Front Housing for Easy Relamping
- Mogul-Base Socket
- Mounting Yoke
- Lamp Included in all models
- Suitable for Wet Locations



Cat. No.	Lamp	Lumens	CRI	Wattage	Ballast	UPC
HFL5-HPS250	High-Pressure Sodium	28000 lm	22	250W	120/208/240/277V Quad Tap CWA	615624373098
HFL5-HPS400	High-Pressure Sodium	51000 lm	22	400W	120/208/240/277V Quad Tap CWA	615624373104
HFL5-MH250-PS	Metal Halide	19100 lm	65	250W	120/208/240/277V Quad Tap CWA	615624387385
HFL5-MH400-PS	Metal Halide	33100 lm	65	400W	120/208/240/277V Quad Tap CWA	615624376334





Catalog#: HL38 SERIES
BULLET FLOODLIGHT W/ IN-GROUND BALLAST GEAR

Category


Line Voltage

Page

[H31](#)

Features:

- Cast Aluminum Housing
- Tempered Clear Glass Lens
- Powder Coated Finish
- Premium Grade Porcelain Socket with Nickel contacts and Teflon-jacketed wire leads
- Pre-wired with 24" SPT-1 Cord
- Sealed with High Grade Weatherproof Silicone Gasket
- Metal Halide Lamp
- Fiberglass Underground Junction Box Included [\[UGJB\]](#)
- Lamp Included in all models
- Suitable for Wet Locations



Cat. No.	Lamp	Lumens	CRI	Wattage	Ballast	Finish	UPC
HL38-MH70	Metal Halide	5500 lm	65	70W	120/208/240/277V Quad Tap CWA	Black	615624373432
						Brown	615624373449
						Green	615624373463
						White	615624373470
HL38-MH100	Metal Halide	6200 lm	65	100W	120/208/240/277V Quad Tap CWA	Black	615624373388
						Brown	615624373395
						Green	615624373418
						White	615624373425





Catalog#: FGS-4
GLARE SHIELD FOR HFL4 FLOOD

Category

Line Voltage

Page

[H32](#)

Description:

Optional Glare Shield for [HFL4](#)

Specifications:

Material

Stamped Aluminum

Cat. No.	UPC
FGS-4	615624373005





Catalog#: FGS-5
GLARE SHIELD FOR HFL5 FLOOD

Category

Line Voltage

Page

[H32](#)

Description:

Optional Glare Shield for [HFL5](#)

Specifications:

Material

Stamped Aluminum

Cat. No.	UPC
FGS-5	615624373012





Catalog#: PMA-HFL
ADJUSTABLE POLE MOUNT ARM FOR HID


Category Line Voltage
Page [H32](#)

Description:

Cast Aluminum Pole Mounting Arm
 For use with [HFL4](#) and [HFL5](#) Floodlights

Features:

- Sturdy Die-Cast Aluminum
- Dark Bronze Polyester Powder-Coat Finish
- Gaskets and Mounting Bolts Included
- Adjustable Direct Pole
- Mounting Arm, 180° Adjustability



Specifications:

Material Cast Aluminum

Cat. No.	UPC
PM-HFL	615624375184






Catalog#: PM-HFL
POLE-MOUNT ARM FOR HID SHOE BOX

Category Line Voltage
Page [H32](#)

Description:

Cast Aluminum Pole Mounting Arm
 For use with [HFL4](#) and [HFL5](#) Floodlights



Features:

- Sturdy Die-Cast Aluminum
- Dark Bronze Polyester Powder-Coat Finish
- Gaskets and Mounting Bolts Included
- Adjustable Direct Pole

Specifications:

Material Cast Aluminum

Cat. No.	UPC
PM-HFL	615624375184





Catalog#: SF-HFL
SLIP FITTER FOR HID SHOE BOX


Category Line Voltage
Page [H32](#)

Description:

Adjustable Slip-Fitter
 For use with [HFL4](#) and [HFL5](#) Floodlights
 Fits over 2-3/8" O.D. Pipe

Features:

- Sturdy Die-Cast Aluminum
- Dark Bronze Polyester Powder-Coat Finish
- 180° Adjustability
- Mounting Bolts Included
- Mounts Externally
- No need to open fixture



Specifications:

Material Cast Aluminum

Cat. No.	UPC
SF-HFL	615624375177





Catalog#: UGJB
FIBERGLASS UNDERGROUND JUNCTION BOX

Category

Line Voltage

Page

[H32](#)



Description:

Optional Fiberglass Underground Junction Box Without Ballast Gear for [HL38-MH70](#) and [HL38-MH100](#)

Specifications:

Finish

Bronze



Cat. No.	UPC
UGJB	615624374309






Catalog#: HCM1 SERIES
SQ. CANOPY CEILING MOUNT LIGHT

Category Line Voltage
Page [H33](#)

Description:

- Pulse Start on Select Models
- Cast Aluminum Housing
- Polycarbonate Lens
- Premium Grade Porcelain Socket
- Sealed with High Grade Weatherproof Silicone Gasket
- Pre-wired Teflon-jacketed 9" Pigtail
- Powder Coated Textured Bronze Finish
- Medium Base E26 Socket
- Lamp Included in both models
- Suitable for Damp Locations



Cat. No.	Lamp	Lumens	CRI	Wattage	Ballast	UPC
HCM1-MH175-PS	Metal Halide	11700 lm	65	175W	120/208/240/277V Quad CWA	615624376372
HCM1-HPS150	High-Pressure Sodium	16000 lm	22	150W	120V NPF	615624375207





**Catalog#: HCM3 SERIES
 DELUXE GARAGE LIGHT**

Category


Line Voltage

Page

[H33](#)

Description:

- Pulse Start on Select Models
- Cast Aluminum Housing
- Deluxe Garage Light
- Removable Upper Aluminum Reflector
- Band to illuminate ceiling
- Polycarbonate Reflector
- Round Cast Aluminum Housing
- Premium Grade Porcelain Socket
- Sealed with High Grade Weatherproof Silicone Gasket
- Pre-wired Teflon-jacketed 9" Pigtail
- Powder Coated Finish
- Medium Base E26 Socket for HPS & MH models
- Lamp Included in all models
- Suitable for Damp Locations



Cat. No.	Lamp	Lumens	CRI	Wattage	Ballast	UPC
HCM3-MH175-PS	Metal Halide	11700 lm	65	175W	Quad Tap CWA	615624387125
HCM3-HPS150	High-Pressure Sodium	16000 lm	22	150W	Quad Tap CWA	615624373043
HCM3-PL84	2 X PL42	6000 lm	82	42W	Electronic Ballast	615624373074



HHB1-MH400-PS

Descriptions

Orbit Industries provides the HHB1-MH400-PS temporary light for work sites. The quick installation allows for immediate lighting on all jobs.


General Specifications

- ▶ Mogul Base 400W Pulse start Metal Halide provides 33100 Lumens, 82+ CRI
- ▶ Easily attachable 10" welded 11 ga. Steel wire guard mounts directly to the body to protect lamp from accidental impact
- ▶ Quad Tap Ballast: 120/208/240/277V, Wired at 120V
- ▶ Complies with NEC 2010 for Open-Rated Socket
- ▶ Includes Mogul Based Open-Rated EX39 Lamp
- ▶ Cast Aluminum Construction
- ▶ 11 ga. Hook with Locking feature
- ▶ Low profile to keep out of the way on jobsite
- ▶ 2 - 3/4" knock-outs for conduit installation
- ▶ Quick and Easy to assemble
- ▶ Optional bottom tray included
- ▶ 3 ft cord




HHB1-MH400-PS

Dimensions



Accessory

- ▶ 11 ga. Steel Wire Guard



HHB1-WG2

Item No.	Description	Std. Pkg.
HHB1-MH400-PS	ALL IN ONE CONST. LIGHT MH400 120~277V PULSE START	1
HHB1-WG2	WIRE GUARD FOR HHB1	5





Catalog#: HHB1-WG
WIRE GUARD FOR HHB1

Category

Line Voltage

Page

[H34](#)

Description:

Chrome Steel Wire Guard

Cat. No.	UPC
HHB1-WG	615624001120





Catalog#: HHB1-WG2
CHROME STEEL WIRE GUARD

Category

Line Voltage

Page

[H34](#)

Description:

Chrome Steel Wire Guard

Cat. No.	UPC
HHB1-WG2	615624001151





**Catalog#: HHB2 SERIES
 HIGH/LOW BAY BALLASTS**

Category Line Voltage
Page [H35](#)

Description:

- Pulse Start on Select Models
- Hook Included
- Order Dome and Accessories Separately

Features:

- Premium Grade Porcelain Socket - 5KV Pulse Rated
- Pre-wired 36" 16/3 600V Cord



Cat. No.	Lamp	Ballast	Wattage	UPC
HHB2-MH400	Mogul Base Metal Halide	120/208/240/277V Quad Tap CWA	400W	615624375948
HHB2-MH400-PS			400W	615624376365
HHB2-MH250-PS			250W	615624376358





Catalog#: HHB2-ACR16
16" Prismatic Acrylic Reflector Dome

Category

Line Voltage

Page

[H35](#)

Description:

16" Prismatic Acrylic Reflector Dome,
Requires HHB2-CO16 Collar for Installation (Sold Separately)

Cat. No.	UPC
HHB2-ACR16	615624387712





Catalog#: HHB2-ACR22
22" Prismatic Acrylic Reflector Dome

Category

Line Voltage

Page

[H35](#)

Description:

22" Prismatic Acrylic Reflector Dome,
Requires HHB2-CO22 Collar for Installation (Sold Separately)

Cat. No.	UPC
HHB2-ACR22	615624387729





Catalog#: HHB2-AR16
16" Aluminum Reflector Dome

Category

Line Voltage

Page

[H35](#)

Description:

16" Aluminum Reflector Dome

Cat. No.	UPC
HHB2-AR16	615624387736





Catalog#: HHB2-AR16WH
16" WH POWDER-COATED ALUM REFLECTOR DOME

Category

Line Voltage

Page

[H35](#)

Description:

16" White Powder Coated Aluminum Reflector Dome

Cat. No.	UPC
HHB2-AR16WH	615624387743





Catalog#: HHB2-AR22
22" Aluminum Reflector Dome

Category

Line Voltage

Page

[H35](#)

Description:

22" Aluminum Reflector Dome

Cat. No.	UPC
HHB2-AR22	615624387750





Catalog#: HHB2-AR22WH

22" WH POWDER-COATED ALUMINUM REFLECTOR DOME

Category

Line Voltage

Page

[H35](#)

Description:

22" White Powder Coated Aluminum Reflector Dome

Cat. No.	UPC
HHB2-AR22WH	615624387767





Catalog#: HHB2-ACDL
ACRYLIC DROP LENS FOR HIGH/LOW BAY

Category Line Voltage
Page [H36](#)

Description:

16" or 22" Acrylic Drop Lens
 Clamp Band Required for Installation, Sold Separately

Cat. No.	UPC
HHB2-ACDL16	615624373135
HHB2-ACDL22	615624373142





Catalog#: HHB2-CB
CLAMP BAND FOR HIGH/LOW BAY

Category

Line Voltage

Page

[H36](#)

Description:

16" or 22" Clamp Band

Cat. No.	UPC
HHB2-CB16	615624373159
HHB2-CB22	615624373166





**Catalog#: HHB2-CH
CAST HOOK**

Category

Line Voltage

Page


[H36](#)

Description:

Cast Hook

Cat. No.	UPC
HHB2-CH	615624001137





Catalog#: HHB2-CO16
Collar for 16" Prismatic Dome

Category

Line Voltage

Page


[H36](#)

Description:

Collar for 16" Prismatic Dome

Cat. No.	UPC
HHB2-CO16	615624387774





Catalog#: HHB2-CO22
Collar for 22" Prismatic Dome

Category

Line Voltage

Page

[H36](#)

Description:

Collar for 22" Prismatic Dome

Cat. No.	UPC
HHB2-CO22	615624387781





Catalog#: HHB2-GL
GLASS LENS FOR HIGH/LOW BAY

Category

Line Voltage

Page

[H36](#)

Description:

16" or 22" Tempered Glass Lens with Rubber Gasket
(Clamp Band Required for Installation, Sold Separately)

Cat. No.	UPC
HHB2-GL16	615624373173
HHB2-GL22	615624373180





Catalog#: HHB2-WG
WIRE GUARD FOR HIGH/LOW BAY

Category

Line Voltage

Page

[H36](#)

Description:

16" or 22" Wire Guard, Chrome Steel

Cat. No.	UPC
HHB2-WG16	615624373197
HHB2-WG22	615624373203





Catalog#: BAL500
EMERG. BALLAST 500 LUMENS

Category	Line Voltage
Page	F23 / H38
Barcode	6-15624-87264-5

Features:

- 120/277 VAC, Fully Automatic Operation
- 280mA Charging Current
- 24Hr Recharging Time
- 90 min of Emergency Operation
- Wireway or Fixture Mount
- Battery, Charger, Inverter Circuit in a Single Package

Specifications:

Compatible with most One-, Two-, Three-, and Four-Lamp Electronic Standard and Dimming AC Ballasts


Operates:

- One 17W - 40W T8 - T12,
- One 13W - 26W 4-Pin Compact
- One 18W - 36W 4-Pin Long Compact Fluorescent Lamp

Packaging Info:

Std Pkg	1
Weight	11

Line Drawings:





Catalog#: BAL650C-2PIN
EMERG. BALLAST 650 LUMENS RECESS 2-PIN

Category	Line Voltage
Page	F23 / H38
Barcode	6-15624-87263-8

Features:

- 120/277 VAC, Fully Automatic Operation
- 280mA Charging Current
- 24Hr Recharging Time
- 90 min of Emergency Operation
- Wireway or Fixture Mount
- Battery, Charger, Inverter Circuit in a Single Package

Specifications:

Compatible with most One-, Two-, Three-, and Four-Lamp Electronic Standard and Dimming AC Ballasts


Operates:

- One 13W - 26W
- 2-Pin Compact Fluorescent Lamps with GX23 and G24D Bases

Packaging Info:

Std Pkg	1
Weight	19

Line Drawings:





Catalog#: BAL650C-4PIN
EMERG. BALLAST 650 LUMENS RECESS 4-PIN

Category	Line Voltage
Page	F23 / H38
Barcode	6-15624-87318-5

Features:

- 120/277 VAC, Fully Automatic Operation
- 280mA Charging Current
- 24Hr Recharging Time
- 90 min of Emergency Operation
- Wireway or Fixture Mount
- Battery, Charger, Inverter Circuit in a Single Package

Specifications:

Compatible with most One-, Two-, Three-, and Four-Lamp Electronic Standard and Dimming AC Ballasts


Operates:

- One 13W - 42W
- Two 13W - 39W Twin, Quad, Triple Twin Long Compacts or 2D Lamps

Packaging Info:

Std Pkg	1
Weight	20.5

Line Drawings:





Catalog#: BAL700
EMERG. BALLAST 700 LUMENS

Category	Line Voltage
Page	F24 / H39
Barcode	6-15624-87265-2

Features:

- 120/277 VAC, Fully Automatic Operation
- 280mA Charging Current
- 24Hr Recharging Time
- 90 min of Emergency Operation
- Wireway or Fixture Mount
- Battery, Charger, Inverter Circuit in a Single Package

Specifications:

Compatible with most One-, Two-, Three-, and Four-Lamp Electronic Standard and Dimming AC Ballasts


Operates:

- Two 17W - 40W
- One 17W - 110W T8 - T12
- Two 13W - 39W
- One 13W - 42W 4-Pin Compact
- One 18W - 50W 4-Pin Long Compact Fluorescent Lamp

Packaging Info:

Std Pkg	1
Weight	13

Line Drawings:





Catalog#: BAL1400
EMERG. BALLAST 1400 LUMENS

Category	Line Voltage
Page	F24 / H39
Barcode	6-15624-87266-9

Features:

- 120/277 VAC, Fully Automatic Operation
- 280mA Charging Current
- 24Hr Recharging Time
- 90 min of Emergency Operation
- Wireway or Fixture Mount
- Battery, Charger, Inverter Circuit in a Single Package

Specifications:

Compatible with most One-, Two-, Three-, and Four-Lamp Electronic Standard and Dimming AC Ballasts


Operates:

- Two 17W - 40W
- One 17W - 110W T8 - T12
- Two 13W - 39W
- One 13W - 42W 4-Pin Compact
- Two 18W - 36W
- One 18W - 50W 4-Pin Long Compact Fluorescent Lamp

Packaging Info:

Std Pkg	1
Weight	18

Line Drawings:





Catalog#: BAL3000
EMERG. BALLAST 3000 LUMENS

Category	Line Voltage
Page	F24 / H39
Barcode	6-15624-87267-6

Features:

- 120/277 VAC, Fully Automatic Operation
- 280mA Charging Current
- 24Hr Recharging Time
- 90 min of Emergency Operation
- Wireway or Fixture Mount
- Battery, Charger, Inverter Circuit in a Single Package

Specifications:

Compatible with most One-, Two-, Three-, and Four-Lamp Electronic Standard and Dimming AC Ballasts


Operates:

- Two 17W - 40W
- One 17W - 215W T8 - T12
- Two 13W - 42W 4-Pin Compact
- Two 18W - 36W
- One 18W - 55W 4-Pin Long Compact Fluorescent Lamp

Packaging Info:

Std Pkg	1
Weight	54

Line Drawings:





**Catalog#: BAL50HPSKIT
50W-HPS BALLAST KIT**

Category	Line Voltage
Page	H40
Barcode	6-15624-37581-8

Description:

Ballast & Ignitor

Specifications:

Lamp type	High Pressure Sodium
Wattage	50W Non UL
Voltage	120V

Packaging Info:

Std Pkg	1
Weight	0.3





Catalog#: BAL70HPSKIT
70W-HPS BALLAST KIT

Category	Line Voltage
Page	H40
Barcode	6-15624-37582-5

Description:

Ballast & Ignitor

Specifications:

Lamp type	High Pressure Sodium
Wattage	70W
Voltage	120V

Packaging Info:

Std Pkg	1
Weight	0.3





Catalog#: BAL70MHKIT
70W-MH BALLAST KIT

Category	Line Voltage
Page	H40
Barcode	6-15624-37586-3

Description:

Ballast & Ignitor & Capacitor

Specifications:

Lamp type	Metal Halide
Wattage	70W
Voltage	120~277V

Packaging Info:

Std Pkg	1
Weight	0.3





Catalog#: BAL100MHKIT
100W-MH BALLAST KIT

Category	Line Voltage
Page	H40
Barcode	6-15624-37587-0

Description:

Ballast & Ignitor & Capacitor

Specifications:

Lamp type	Metal Halide
Wattage	100W
Voltage	120~277V

Packaging Info:

Std Pkg	1
Weight	0.3





Catalog#: BAL150HPSKIT
150W-HPS BALLAST KIT

Category	Line Voltage
Page	H40
Barcode	6-15624-37583-2

Description:

Ballast & Ignitor

Specifications:

Lamp type	High Pressure Sodium
Wattage	150W
Voltage	120V

Packaging Info:

Std Pkg	1
Weight	0.3





**Catalog#: BAL150MH-PSKIT
150W-MH-PS BALLAST KIT**

Category	Line Voltage
Page	H40
Barcode	6-15624-38808-5

Description:

Ballast & Ignitor & Capacitor

Specifications:

Lamp type	Metal Halide-Pulse Start
Wattage	150W
Voltage	120~277V

Packaging Info:

Std Pkg	1
Weight	0.3





Catalog#: BAL175MHKIT
175W-MH BALLAST KIT

Category	Line Voltage
Page	H40
Barcode	6-15624-37588-7

Description:

Ballast & Ignitor & Capacitor

Specifications:

Lamp type	Metal Halide
Wattage	175W
Voltage	120~277V

Packaging Info:

Std Pkg	1
Weight	0.3





Catalog#: BAL250HPSKIT
250W-HPS BALLAST KIT

Category	Line Voltage
Page	H40
Barcode	6-15624-37584-9

Description:

Ballast & Ignitor

Specifications:

Lamp type	High Pressure Sodium
Wattage	250W
Voltage	120~277V

Packaging Info:

Std Pkg	1
Weight	0.3





Catalog#: BAL250MHKIT
250W-MH BALLAST KIT

Category	Line Voltage
Page	H40
Barcode	6-15624-37589-4

Description:

Ballast & Ignitor & Capacitor

Specifications:

Lamp type	Metal Halide
Wattage	250W
Voltage	120~277V

Packaging Info:

Std Pkg	1
Weight	0.3





**Catalog#: BAL250MH-PSKIT
250W-MH-PS BALLAST KIT**

Category	Line Voltage
Page	H40
Barcode	6-15624-37648-8

Description:

Ballast & Ignitor & Capacitor

Specifications:

Lamp type	Metal Halide-Pulse Start
Wattage	250W
Voltage	120~277V

Packaging Info:

Std Pkg	1
Weight	0.3





Catalog#: BAL400HPSKIT
400W-HPS BALLAST KIT

Category	Line Voltage
Page	H40
Barcode	6-15624-37585-6

Description:

Ballast & Ignitor

Specifications:

Lamp type	High Pressure Sodium
Wattage	400W
Voltage	120~277V

Packaging Info:

Std Pkg	1
Weight	0.3





Catalog#: BAL400MHKIT
400W-MH BALLAST KIT

Category	Line Voltage
Page	H40
Barcode	6-15624-37590-0

Description:

Ballast & Ignitor & Capacitor

Specifications:

Lamp type	Metal Halide
Wattage	400W
Voltage	120~277V

Packaging Info:

Std Pkg	1
Weight	0.3





Catalog#: BAL400MH-PSKIT
400W MH-PS BALLAST KIT

Category	Line Voltage
Page	H40
Barcode	6-15624-37649-5

Description:

Ballast & Ignitor & Capacitor

Specifications:

Lamp type	Metal Halide-Pulse Start
Wattage	400W
Voltage	120~277V

Packaging Info:

Std Pkg	1
Weight	0.3





Catalog#: LET-60-GW
ELECTRONIC TRANSFORMERS

Category	Landscape Lighting
Page	G45, H41
Barcode	6-15624-35759-3

Description:

LET 60 AC 120 12 CL2 Ground Wire has a ground wire with lug and double-sided tape attached to the back of the transformer

Packaging Info:

Std Pkg	1
Weight	





Catalog#: LET-60-LW
ELECTRONIC TRANSFORMERS

Category	Landscape Lighting
Page	G45, H41
Barcode	6-15624-38758-3

Description:

LET 60 AC 120 12 CL2 Low Watt has a low minimum connected load requirement of only 2.9W

Packaging Info:

Std Pkg	1
Weight	





Catalog#: LET-75
ELECTRONIC TRANSFORMERS

Category	Landscape Lighting
Page	G45, H41
Barcode	6-15624-38761-3

Description:

LET 75 AC 120 12 Standard 75W transformer

Packaging Info:

Std Pkg	1
Weight	





Catalog#: LET-75-277
ELECTRONIC TRANSFORMERS

Category	Landscape Lighting
Page	G45, H41
Barcode	6-15624-38802-3

Description:

LET 75 AC 277 12 Standard 75W transformer

Packaging Info:

Std Pkg	1
Weight	





Catalog#: LET-75-LV
ELECTRONIC TRANSFORMERS

Category	Landscape Lighting
Page	G45, H41
Barcode	6-15624-38762-0

Description:

LET 75 AC 120 11.3V has a Reduced Output Voltage of 11.3V

Packaging Info:

Std Pkg	1
Weight	





Catalog#: LET-151-12
ELECTRONIC TRANSFORMERS

Category	Landscape Lighting
Page	G45, H41
Barcode	6-15624-38763-7

Description:

LET 151 AC 120 12R, 150W with 12V Output, Standard Version

Packaging Info:

Std Pkg	1
Weight	





Catalog#: LET-303-12-AC
ELECTRONIC TRANSFORMERS

Category	Landscape Lighting
Page	G45, H41
Barcode	6-15624-38765-1

Description:

LET 303 AC 120 12 Rectangular Shape

Packaging Info:

Std Pkg	1
Weight	





Catalog#: LVT-60
ELECTRONIC TRANSFORMERS

Category	Landscape Lighting
Page	G45, H41
Barcode	6-15624-38760-6

Description:

LVT 60 AC 120 12 CL2 has a 60W transformer mounting within an enclosure, for remote mounting

Packaging Info:

Std Pkg	1
Weight	





Catalog#: LVT-303-12-AC
ELECTRONIC TRANSFORMERS

Category	Landscape Lighting
Page	G45, H41
Barcode	6-15624-38766-8

Description:

LVT 303 AC 120 12, 300W Transformer with 12V output
mounted within an enclosure, rectangular shape, for remote mounting

Packaging Info:

Std Pkg	1
Weight	





Catalog#: 40T10
40W MED. BASE T10 LAMP

Category	Line Voltage
Page	H42
Barcode	6-15624-26955-1

Description:

Medium Base Lamp for Step Lights

Specifications:

Voltage	120V
Wattage	40W
Base	E26
Life hours	1000

Packaging Info:

Std Pkg	10
Weight	





Catalog#: 50JDR16
50W 120V JDR16 FLOOD

Category	Line Voltage
Page	H42
Barcode	6-15624-26724-3

Description:

JDR16 Halogen, 40° Flood

Specifications:

Voltage	120V
Wattage	50W
Base	E26
Life hours	2000

Packaging Info:

Std Pkg	10
Weight	





Catalog#: 100T4
100W 120V T4 HALOGEN BULB

Category	Line Voltage
Page	H42
Barcode	6-15624-37356-2

Description:

Halogen Lamp

Specifications:

Voltage	120V
Wattage	100W
Base	G8
Life hours	12000

Packaging Info:

Std Pkg	10
Weight	





Catalog#: JC-20-120V
20W 120V JC LAMP

Category	Line Voltage
Page	H42
Barcode	6-15624-37349-4

Description:

JC Halogen

Specifications:

Voltage	120V
Wattage	20W
Base	GY6.35
Life hours	1500

Packaging Info:

Std Pkg	20
Weight	





Catalog#: JC-50-120V
50W 120V JC LAMP

Category	Line Voltage
Page	H42
Barcode	6-15624-26388-7

Description:

JC Halogen

Specifications:

Voltage	120V
Wattage	20W
Base	GY6.35
Life hours	1500

Packaging Info:

Std Pkg	20
Weight	






**Catalog#: LA19-7W
 LED A19 Light Bulb**

Category LED
Page [116 / 64](#) (LED Catalog)

Specifications:

Wattage: 7 W
 Voltage: 120 V
 Lens Type: Frosted
 Base: E26/E27
 Housing: Die Cast Aluminum
 Operating Temp: -20°C to +40°C
 Life Hours: 50,000
 Beam Angle: 75°
 Lens Material: Tempered Glass
 Equivalent Wattage Rating: 40W Incandescent A19
 Certification



Catalog Number	UPC	Efficacy	Color Temperature	Emission Color	Lumens	CRI
LA19-7W-WW	615624376556	42 lm/W	3000K	Warm White	300 lm	75






Catalog#: LA19-8W-D
LED A19 Light Bulb

Category LED
Page [116 / 64](#) (LED Catalog)

Specifications:

Wattage: 8 W
 Voltage: 120 V
 Lens Type: Frosted
 Base: E26/E27
 Housing: Die Cast Aluminum
 Operating Temp: -20°C to +40°C
 Life Hours: 50,000
 Beam Angle: 75°
 Lens Material: Tempered Glass
 Equivalent Wattage Rating: 50W Incandescent A19
 Certification



Catalog Number	UPC	Efficacy	Color Temperature	Emission Color	Lumens	CRI
LA19-8W-D-WW	615624387989	46 lm/W	3000K	Warm White	300 lm	80
LA19-8W-D-CW	615624387972	51 lm/W	4700K	Cool White	410 lm	75






Catalog#: LMR16-3W-EB
MR16 LED Flood Light

Category LED
Page [115 / 63](#) (LED Catalog)

Specifications:

Wattage: 3W
 Voltage: 120V
 Lens Type: Frosted
 Base: E26/E27
 Housing: Die Cast Aluminum
 Operating Temp: -20°C to +40°C
 Life Hours: 50,000
 Beam Angle: 30°
 Lens Material: Acrylic
 Equivalent Wattage Rating: 20W Halogen MR16
 Certification



Catalog Number	UPC	Efficacy	Color Temperature	Emission Color	Lumens	CRI
LMR16-3W-EB-WW	615624387675	63 lm/W	3000K	Warm White	190 lm	70






Catalog#: LMR16-4W-EB
LED MR16 Flood Light

Category LED
Page [115 / 63](#) (LED Catalog)

Specifications:

Wattage: 4 W
 Voltage: 120 V
 Lens Type: Frosted
 Base: E26/E27
 Housing: Die Cast Aluminum
 Operating Temp: -20°C to +40°C
 Life Hours: 50,000
 Beam Angle: 25°
 Lens Material: Acrylic
 Equivalent Wattage Rating: 20W Halogen MR16
 Certification



Catalog Number	UPC	Efficacy	Color Temperature	Emission Color	Lumens	CRI
LMR16-4W-EB-WW	615624387965	42 lm/W	3000K	Warm White	170 lm	80
LMR16-4W-EB-CW	615624387958	50 lm/W	4700K	Cool White	200 lm	75






Catalog#: LPAR20-8W-D
LED PAR20 Light Bulb

Category LED
Page [117 / 65](#) (LED Catalog)

Specifications:

Wattage: 8 W
 Voltage: 120 V
 Lens Type: Frosted
 Base: E26/E27
 Housing: Die Cast Aluminum
 Operating Temp: -20°C to +40°C
 Life Hours: 50,000
 Beam Angle: 60°
 Lens Material: Acrylic
 Equivalent Wattage Rating: 50W Incandescent PAR20
 Certification



Catalog Number	UPC	Efficacy	Color Temperature	Emission Color	Lumens	CRI
LPAR20-8W-D-WW	615624387927	43 lm/W	3000K	Warm White	350 lm	80
LPAR20-8W-D-CW	615624387910	48 lm/W	4700K	Cool White	390 lm	75






Catalog#: LPAR30-12W-D
LED PAR30 Light Bulb

Category LED
Page [117 / 65](#) (LED Catalog)

Specifications:

Wattage: 12 W
 Voltage: 120 V
 Lens Type: Frosted
 Base: E26/E27
 Housing: Die Cast Aluminum
 Operating Temp: -20°C to +40°C
 Life Hours: 50,000
 Beam Angle: 60°
 Lens Material: Acrylic
 Equivalent Wattage Rating: 50W Incandescent PAR30
 Certification



Catalog Number	UPC	Efficacy	Color Temperature	Emission Color	Lumens	CRI
LPAR30-12W-D-WW	615624387903	50 lm/W	3000K	Warm White	590 lm	80
LPAR30-12W-D-CW	615624387897	50 lm/W	4700K	Cool White	600 lm	75






Catalog#: LPAR30-13W
LED PAR30 Light Bulb

Category LED
Page [17](#)

Specifications:

Wattage: 13 W
 Voltage: 120 V
 Lens Type: Frosted
 Base: E26/E27
 Housing: Die Cast Aluminum
 Operating Temp: -20°C to +40°C
 Life Hours: 50,000
 Beam Angle: 30°
 Lens Material: Acrylic
 Equivalent Wattage Rating: 50W Incandescent PAR30
 Certification



Catalog Number	UPC	Efficacy	Color Temperature	Emission Color	Lumens	CRI
LPAR30-13W-WW	615624376570	41 lm/W	3000K	Warm White	600 lm	85






Catalog#: LPAR38-16W-D
LED PAR38 Light Bulb

Category LED
Page [118 / 66](#) (LED Catalog)

Specifications:

Wattage: 16 W
 Voltage: 120 V
 Lens Type: Prismatic
 Base: E26/E27
 Housing: Die Cast Aluminum
 Operating Temp: -20°C to +40°C
 Life Hours: 50,000
 Beam Angle: 60°
 Lens Material: Acrylic
 Equivalent Wattage Rating: 60W Incandescent PAR38
 Certification



Catalog Number	UPC	Efficacy	Color Temperature	Emission Color	Lumens	CRI
LPAR38-16W-D-WW	615624387941	50 lm/W	3000K	Warm White	800 lm	80
LPAR38-16W-D-CW	615624387934	56 lm/W	4700K	Cool White	900 lm	75






Catalog#: LPAR38-16W-D-OD
Outdoor Rated LED Bulbs

Category LED
Page [118 / 66](#) (LED Catalog)

Specifications:

Wattage: 16 W
 Voltage: 120 V
 Lens Type: Frosted
 Base: E26/E27
 Housing: Die Cast Aluminum
 Operating Temp: -20°C to +40°C
 Life Hours: 50,000
 Beam Angle: 60°
 Lens Material: Acrylic
 Equivalent Wattage Rating: 60W Incandescent PAR38



Outdoor Rated

Certification



Catalog Number	UPC	Efficacy	Color Temperature	Emission Color	Lumens	CRI
LPAR38-16W-D-WW-OD	615624388436	50 lm/W	3000K	Warm White	800 lm	80
LPAR38-16W-D-CW-OD	615624000833	56 lm/W	4700K	Cool White	900 lm	80





Catalog#: MH70/PAR38/FL/4K
ORBIT 70W MH PAR38 LAMP

Category	Line Voltage
Page	H42
Barcode	6-15624-26999-5

Description:

Metal Halide PAR38 Lamp

Specifications:

Voltage	120~277V
Wattage	70W
Base	E26
Life hours	10000

Packaging Info:

Std Pkg	1
Weight	





Catalog#: MH100/PAR38/FL/4K
ORBIT 100W MH PAR38 LAMP

Category	Line Voltage
Page	H42
Barcode	6-15624-26937-7

Description:

Metal Halide PAR38 Lamp

Specifications:

Voltage	120~277V
Wattage	100W
Base	E26
Life hours	10000

Packaging Info:

Std Pkg	1
Weight	





Catalog#: MV160/R40/FL/4K
ORBIT 160W MERCURY VAPOR R40 LAMP

Category	Line Voltage
Page	H42
Barcode	6-15624-26944-5

Description:

R40 Mercury Vapor, Self-Ballast, Flood 4K

Specifications:

Voltage	120V
Wattage	160W
Base	E26
Life hours	10000

Packaging Info:

Std Pkg	6
Weight	





Catalog#: PL9-41K
9W 120V 2-PIN COMPACT FLUORESCENT PL9

Category	Line Voltage
Page	H42
Barcode	6-15624-26680-2

Description:

Compact Fluorescent, 4100K

Specifications:

Voltage	120V
Wattage	9W
Base	G23
Life hours	10000

Packaging Info:

Std Pkg	10
Weight	





Catalog#: PL13-41K
PL13 COMPACT FLUORESCENT 4100K

Category	Line Voltage
Page	H42
Barcode	6-15624-37356-2

Description:

Compact Fluorescent, 4100K

Specifications:

Voltage	120V
Wattage	13W
Base	GX23
Life hours	12000

Packaging Info:

Std Pkg	10
Weight	





Catalog#: PL13-GU-27K
COMPACT FLOURESCENT LAMP, GU24 BASE, 13W, 2700K

Category	Line Voltage
Page	J15
Barcode	6-15624-00507-4

Description:

Compact Fluorescent, 2700K

Specifications:

Voltage	120V
Wattage	13W
Base	GU24
Life hours	10000

Packaging Info:

Std Pkg	1
Weight	





Catalog#: PL23-GU-41K
COMPACT FLOURESCENT LAMP, GU24 BASE, 23W, 4100K

Category	Line Voltage
Page	J15
Barcode	6-15624-00506-7

Description:

Compact Fluorescent, 4100K

Specifications:

Voltage	120V
Wattage	23W
Base	GU24
Life hours	10000

Packaging Info:

Std Pkg	1
Weight	





Catalog#: PLQ9-41K
9W 120V 2-PIN QUAD COMPACT FLUORESCENT PL9

Category	Line Voltage
Page	H42
Barcode	6-15624-26680-2

Description:

Compact Quad Fluorescent, 4100K

Specifications:

Voltage	120V
Wattage	9W
Base	G23.2
Life hours	10000

Packaging Info:

Std Pkg	20
Weight	





Catalog#: PLQ13-41K
PL13 QUAD COMPACT FLUORESCENT 2-PIN

Category	Line Voltage
Page	H42
Barcode	6-15624-26397-9

Description:

Compact Quad Fluorescent, 4100K

Specifications:

Voltage	120V
Wattage	13W
Base	G23.2
Life hours	10000

Packaging Info:

Std Pkg	10
Weight	





Catalog#: PLQ26-41K
PLQ26-41K 26W QUAD COMPACT FLUORESCENT BULB

Category	Line Voltage
Page	H42
Barcode	6-15624-00114-4

Description:

Compact Quad Fluorescent, 4100K

Specifications:

Voltage	120V
Wattage	26W
Base	G24q-3
Life hours	10000

Packaging Info:

Std Pkg	10
Weight	





Catalog#: PLQ42-41K
COMPACT 4PIN FLUORESCENT LAMP 4100K

Category	Line Voltage
Page	H42
Barcode	6-15624-37358-6

Description:

Compact Quad Fluorescent, 4100K

Specifications:

Voltage	120V
Wattage	42W
Base	GX29q-4
Life hours	12000

Packaging Info:

Std Pkg	10
Weight	





Catalog#: PLQ42-65K
COMPACT 4PIN FLUORESCENT LAMP 6500K

Category	Line Voltage
Page	H42
Barcode	6-15624-38726-2

Description:

Compact Quad Fluorescent, 6500K

Specifications:

Voltage	120V
Wattage	42W
Base	GX29q-4
Life hours	12000

Packaging Info:

Std Pkg	10
Weight	





Catalog#: Q150T3/S
150W T3 SHORT QUARTZ LIGHT BULB -CLR

Category	Line Voltage
Page	H42
Barcode	6-15624-26389-4

Description:

J-Type 78mm Short Linear Quartz Halogen

Specifications:

Voltage	120V
Wattage	150W
Base	R7s
Life hours	1500

Packaging Info:

Std Pkg	20
Weight	





Catalog#: Q300T3
300W T3 QUARTZ LIGHT BULB

Category	Line Voltage
Page	H42
Barcode	6-15624-26390-0

Description:

J-Type 118mm Linear Quartz Halogen

Specifications:

Voltage	120V
Wattage	300W
Base	R7s
Life hours	1500

Packaging Info:

Std Pkg	20
Weight	





Catalog#: Q500T3
500W T3 QUARTZ LIGHT BULB

Category	Line Voltage
Page	H42
Barcode	6-15624-26391-7

Description:

J-Type 118mm Linear Quartz Halogen

Specifications:

Voltage	120V
Wattage	500W
Base	R7s
Life hours	1500

Packaging Info:

Std Pkg	20
Weight	





Catalog#: Q1000T3
1000W JUMBO QUARTZ LAMP 120V DOUBLE EN

Category	Line Voltage
Page	H42
Barcode	6-15624-26889-9

Description:

J-Type 260mm Linear Quartz Halogen

Specifications:

Voltage	120V
Wattage	1000W
Base	R7s
Life hours	1500

Packaging Info:

Std Pkg	20
Weight	





Catalog#: Q1500T3
1500W JUMBO QUARTZ LAMP 120V DOUBLE EN

Category	Line Voltage
Page	H42
Barcode	6-15624-26392-4

Description:

J-Type 260mm Linear Quartz Halogen

Specifications:

Voltage	120V
Wattage	1500W
Base	R7s
Life hours	1500

Packaging Info:

Std Pkg	20
Weight	





Catalog#: Q1500T3-240
1500W JUMBO QUARTZ LAMP 240V DOUBLE EN

Category	Line Voltage
Page	H42
Barcode	6-15624-26393-1

Description:

J-Type 260mm Linear Quartz Halogen

Specifications:

Voltage	240V
Wattage	1500W
Base	R7s
Life hours	1500

Packaging Info:

Std Pkg	20
Weight	





Catalog#: R30-GU-41K
COMPACT FLOURESCENT LAMP PAR30, GU24 BASE, 16W, 4100K

Category	Line Voltage
Page	J15
Barcode	6-15624-00509-8

Description:

Compact Fluorescent Lamp PAR30, 4100K


Specifications:

Voltage	120V
Wattage	16W
Base	GU24
Life hours	10000

Packaging Info:

Std Pkg	1
Weight	





Catalog#: UCL-12
12" UNDER CABINET LIGHT 8W ELECTRONIC

Category	LIGHTING
Page	F25 , H44
Barcode	6-15624-87268-3

Dimensions:

Width	12"
Height	5"
Depth	1"

Features:

- 12" Under Cabinet Electronic Ballast
- One 8W T5 Fluorescent Lamp
- 120~125 VAC
- Electronic Class P Ballast
- Switch Included
- Heavy Gage Steel with Flush Ends
- K.O.s on Top, Sides, and Back
- Backed White Enamel With Rust Inhibiting Phosphate Coat


Specifications:

Color	White
-------	-------

Packaging Info:

Std Pkg	1
Weight	1.675

Line Drawings:





Catalog#: UCL-21
21" UNDER CABINET LIGHT 13W ELECTRONIC

Category	LIGHTING
Page	F25 , H44
Barcode	6-15624-87269-0

Dimensions:

Width	21"
Height	5"
Depth	1"

Features:

- 21" Under Cabinet Electronic Ballast
- One 13W T5 Fluorescent Lamp
- 120~125 VAC
- Electronic Class P Ballast
- Switch Included
- Heavy Gage Steel with Flush Ends
- K.O.s on Top, Sides, and Back
- Backed White Enamel With Rust Inhibiting Phosphate Coat


Specifications:

Color	White
-------	-------

Packaging Info:

Std Pkg	1
Weight	3

Line Drawings:





Catalog#: UCL-24
24" UNDER CABINET LIGHT 16W ELECTRONIC

Category	LIGHTING
Page	F25 , H44
Barcode	6-15624-87270-6

Dimensions:

Width	24"
Height	5"
Depth	1"

Features:

24" Under Cabinet Electronic Ballast
 Two 8W T5
 120~125 VAC
 Electronic Class P Ballast
 Switch Included
 Heavy Gage Steel with Flush Ends
 K.O.s on Top, Sides, and Back
 Backed White Enamel With Rust Inhibiting Phosphate Coat


Specifications:

Color	White
-------	-------

Packaging Info:

Std Pkg	1
Weight	3.625

Line Drawings:





Catalog#: UCL-33
33" UNDER CABINET LIGHT 21W ELECTRONIC

Category	LIGHTING
Page	F25 , H44
Barcode	6-15624-87271-3

Dimensions:

Width	33"
Height	5"
Depth	1"

Features:

33" Under Cabinet Electronic Ballast
 One 8W T5 & One 12W T5
 120~125 VAC
 Electronic Class P Ballast
 Switch Included
 Heavy Gage Steel with Flush Ends
 K.O.s on Top, Sides, and Back
 Backed White Enamel With Rust Inhibiting Phosphate Coat


Specifications:

Color	White
-------	-------

Packaging Info:

Std Pkg	1
Weight	4.875

Line Drawings:





Catalog#: UCL-42
42" UNDER CABINET LIGHT 26W ELECTRONIC

Category	LIGHTING
Page	F25 , H44
Barcode	6-15624-87272-0

Dimensions:

Width	42"
Height	5"
Depth	1"

Features:

- 42" Under Cabinet Electronic Ballast
- Two 13W T5
- 120~125 VAC
- Electronic Class P Ballast
- Switch Included
- Heavy Gage Steel with Flush Ends
- K.O.s on Top, Sides, and Back
- Backed White Enamel With Rust Inhibiting Phosphate Coat

Specifications:

Color	White
-------	-------

Packaging Info:

Std Pkg	1
Weight	5.2

Line Drawings:

