



2013 GERBER PRODUCT REFERENCE GUIDE

 **GERBER**  
ESSENTIALS



 **GERBER**  
OUTDOOR



 **GERBER**  
SURVIVAL



 **GERBER**  
HUNTING



 **GERBER**  
TACTICAL



 **GERBER**  
INDUSTRIAL





**FOR IN THE TRUCK, THE SHOP, OR YOUR POCKET,** Gerber Essentials are the tools and knives that get us out of unexpected jams every single day. They're the pocket-tools, multi-pliers and everyday carriers that we reach for over and over. Gerber builds them to be durable, lightweight and efficient. What's the specific "activity" for this activity category, you ask? It's Daily Carry.

**ESSENTIALS**

# NEW FOR 2013



		CLAM	CLAM UPC	BOX	BOX UPC	SPECIFICATIONS	
<b>NEW FOR 2013</b>		<b>COHORT™</b>	31-001714	0-13658-13052-4	30-000645	0-13658-13256-6	Blade Length: 3.0" Overall Length: 6.88" Closed Length: 3.88" Weight: 2.6 oz Handle: AL 6061-T6
<b>NEW FOR 2013</b>		<b>CONTRAST™ AO</b>	SERRATED EDGE 31-002269	0-13658-13609-0	30-000784	0-13658-13608-3	Blade Length: 3.0" Overall Length: 7.13" Closed Length: 4.25" Weight: 3.3 oz Handle: G-10 & Stainless Steel 3Cr13
		FINE EDGE 31-001711	0-13658-13050-7	30-000643	0-13658-13255-3		
<b>NEW FOR 2013</b>		<b>COUNTERPART™</b>	31-001719	0-13658-13057-9	30-000647	0-13658-13258-0	Blade Length: 3.00" Overall Length: 7.12" Closed Length: 4.13" Weight: 3.3 oz Handle: G-10
<b>NEW FOR 2013</b>		<b>MINI OUTRIGGER™</b>	31-001759	0-13658-13105-7	30-000688	0-13658-13322-8	Blade Length: 2.5" Overall Length: 5.88" Closed Length: 3.38" Weight: 2.9 oz Handle: Aluminum with SoftGrip Overmold
<b>NEW FOR 2013</b>		<b>OUTRIGGER™</b>	SERRATED EDGE 31-001944	0-13658-13331-0	30-000707	0-13658-13332-7	Blade Length: 3.0" Overall Length: 7.0" Closed Length: 4.0" Weight: 4.16 oz Handle: Aluminum with SoftGrip Overmold
		FINE EDGE 31-001761	0-13658-13108-8	30-000689	0-13658-13325-9		
<b>NEW FOR 2013</b>		<b>OUTRIGGER™ XL</b>	SERRATED EDGE 31-001763	0-13658-13109-5	30-000690	13658-13328-0	Blade Length: 3.38" Overall Length: 7.88" Closed Length: 4.5" Weight: 5.4 oz Handle: Aluminum with SoftGrip Overmold



# NEW FOR 2013

## GDC COLLECTION

[GERBER DAILY CARRY]



NEW FOR 2013



### GDC HOOK KNIFE™

CLAM	CLAM UPC	BOX	BOX UPC
31-001695	0-13658-13024-1	30-000637	0-13658-13249-8

SPECIFICATIONS	
Overall Length:	2"
Closed Length:	3.07"
Weight:	.27 oz
Handle:	6061 T6 Aluminum
Sheath:	Zytel 101

NEW FOR 2013



### GDC TECH SKIN POCKET KNIFE™

CLAM	CLAM UPC	BOX	BOX UPC
31-001693	0-13658-13027-2	30-000636	0-13658-13248-1

SPECIFICATIONS	
Blade Length:	2.52"
Overall Length:	5.93"
Closed Length:	3.4"
Weight:	2.24 oz
Handle:	Zytel 101

NEW FOR 2013



### GDC ZIP BLADE™

CLAM	CLAM UPC	BOX	BOX UPC
31-001742	0-13658-13088-3	30-000661	0-13658-13273-3

SPECIFICATIONS	
Blade Length:	.68"
Overall Length:	2.26"
Closed Length:	1.7"
Steel Type:	7Cr17
Handle:	3Cr13

NEW FOR 2013



### GDC ZIP DRIVER™

CLAM	CLAM UPC	BOX	BOX UPC
31-001738	0-13658-13084-5	30-000659	0-13658-13271-9

SPECIFICATIONS	
Overall Length:	2.15"
Closed Length:	2.15"
Driver Steel Type:	420 Stainless
Handle:	3Cr13

NEW FOR 2013



### GDC ZIP HEX™

CLAM	CLAM UPC	BOX	BOX UPC
31-001740	0-13658-13086-9	30-000660	0-13658-13272-6

SPECIFICATIONS	
Overall Length:	2.1"
Closed Length:	2.1"
Handle:	3Cr13

NEW FOR 2013



### GDC ZIP LIGHT+™

CLAM	CLAM UPC	BOX	BOX UPC
31-001745	0-13658-13090-6	30-000662	0-13658-13274-0

SPECIFICATIONS	
Overall Length:	1.8"
Closed Length:	1.8"
Handle:	3Cr13

# KNIVES










## FOLDING CLIP



		CLAM	CLAM UPC	BOX	BOX UPC	SPECIFICATIONS
	<b>AIR RANGER™</b> SERRATED EDGE	45860	0-13658-45860-4			Blade Length: 3.26" Overall Length: 7.32" Closed Length: 4.06" Weight: 2.6 oz Handle: Aluminum
	<b>AR™ 3.0</b> SERRATED EDGE - BBS FINE EDGE - BB	45864	0-13658-45864-2	05849 05848	0-13658-05849-1 0-13658-05848-4	Blade Length: 3.0" Overall Length: 6.95" Closed Length: 3.95" Weight: 2.8 oz Handle: Aluminum TacHide™
	<b>AR™ 3.0</b> FINE EDGE			05842	0-13658-05842-2	Blade Length: 3.0" Overall Length: 6.95" Closed Length: 3.95" Weight: 2.8 oz Handle: Aluminum TacHide™
	<b>CONTRAST™</b> SERRATED EDGE FINE EDGE	31-000596 31-000595	0-13658-11843-0 0-13658-11841-6	30-000259 30-000258	0-13658-11842-3 0-13658-11840-9	Blade Length: 3.0" Overall Length: 7.12" Closed Length: 4.25" Weight: 3.7 oz Handle: G-10
	<b>E-Z OUT™ JR.</b> SERRATED EDGE FINE EDGE			06551 06501	0-13658-06551-2 0-13658-06501-7	Blade Length: 2.38" Overall Length: 5.48" Closed Length: 3.1" Weight: 1.4 oz Handle: Glass-filled Nylon with TacHide™
	<b>E-Z OUT™ SKELETON</b> SERRATED EDGE FINE EDGE	46751	0-13658-46751-4	06751 06701	0-13658-06751-6 0-13658-06701-1	Blade Length: 3.52" Overall Length: 7.89" Closed Length: 4.56" Weight: 2.6 oz Handle: Glass-filled Nylon with TacHide™
	<b>MINI F.A.S.T. DRAW™</b> SERRATED EDGE FINE EDGE	22-41525 22-41526	0-13658-41525-6 0-13658-41526-3			Blade Length: 2.1" Overall Length: 5.0" Closed Length: 2.9" Weight: 1.9 oz Handle: Glass-filled Nylon
	<b>F.A.S.T. DRAW™</b> SERRATED EDGE FINE EDGE	22-47161 22-47162	0-13658-47161-0 0-13658-47162-7	22-07161 22-07162	0-13658-07161-2 0-13658-07162-9	Blade Length: 2.99" Overall Length: 7.13" Closed Length: 4.14" Weight: 3.6 oz Handle: Glass-filled Nylon
	<b>INSTANT™</b>	31-002184	0-13658-13491-1	30-000752	0-13658-13492-8	Blade Length: 3.18" Overall Length: 7.75" Closed Length: 4.57" Weight: 4.01 oz Handle: G-10



# FOLDING CLIP



	CLAM	CLAM UPC	BOX	BOX UPC	SPECIFICATIONS
	<b>PARAFRAME™ MINI</b> SERRATED EDGE 22-48484 FINE EDGE 22-48485	0-13658-48484-9 0-13658-48485-6	22-08485	0-13658-08485-8	Blade Length: 2.22" Overall Length: 5.25" Closed Length: 3.07" Weight: 1.4 oz Handle: Stainless Steel
	<b>PARAFRAME™ I</b> SERRATED EDGE 22-48443 FINE EDGE 22-48444	0-13658-48443-6 0-13658-48444-3	22-08444	0-13658-08444-5	Blade Length: 3.0" Overall Length: 7.01" Closed Length: 4.01" Weight: 2.6 oz Handle: Stainless Steel
	<b>PARAFRAME™ I - TITANIUM NITRIDE</b> SERRATED EDGE 22-48445 FINE EDGE 22-48446	0-13658-48445-0 0-13658-48446-7	22-08445 22-08446	0-13658-08445-2 0-13658-08446-9	Blade Length: 3.0" Overall Length: 7.01" Closed Length: 4.01" Weight: 2.6 oz Handle: Stainless Steel
	<b>PARAFRAME™ II</b> SERRATED EDGE 22-48447 FINE EDGE 22-48448	0-13658-48447-4 0-13658-48448-1			Blade Length: 3.53" Overall Length: 8.27" Closed Length: 4.74" Weight: 4.2 oz Handle: Stainless Steel
	<b>POWERFRAME™</b> SERRATED EDGE 22-41964 FINE EDGE 22-41965	0-13658-11136-3 0-13658-11138-7			Blade Length: 3.0" Overall Length: 7.0" Closed Length: 4.0" Weight: 3.2 oz Handle: Stainless Steel
	<b>PR™ 2.5</b> FINE EDGE 22-41579	0-13658-41579-9			Blade Length: 2.5" Overall Length: 5.75" Closed Length: 3.25" Weight: 2.8 oz Handle: Glass-Filled Nylon with TacHide™ Inserts
	<b>MINI-REMIX™</b> FINE EDGE 31-000346	0-13658-11529-3			Blade Length: 2.05" Overall Length: 5.6" Closed Length: 3.55" Weight: 2.2 oz Handle: Stainless Steel & Anodized Aluminum
	<b>REMIX™</b> SERRATED EDGE 22-41969 FINE EDGE 22-41968	0-13658-11146-2 0-13658-11144-8			Blade Length: 2.9" Overall Length: 7.35" Closed Length: 4.45" Weight: 4.2 oz Handle: Anodized Aluminum
	<b>RIPSTOP I™</b> SERRATED EDGE 22-41613 FINE EDGE 22-41614	0-13658-41613-0 0-13658-41614-7	22-01614	0-13658-01614-9	Blade Length: 2.3" Overall Length: 5.75" Closed Length: 3.45" Weight: 2.0 oz Handle: Stainless Steel

## FOLDING CLIP



		CLAM	CLAM UPC	BOX	BOX UPC	SPECIFICATIONS
	<b>RIPSTOP II™</b> SERRATED EDGE	22-41616	0-13658-41616-1			Blade Length: 3.0" Overall Length: 7.4" Closed Length: 4.4" Weight: 3.0 oz Handle: Stainless Steel
	<b>VENTURE™</b> SERRATED EDGE	31-001021	0-13658-12521-6	30-000405	0-13658-12520-9	Blade Length: 3.25" Overall Length: 7.8" Closed Length: 4.6" Weight: 4.2 oz Handle: Titanium

## POCKET KNIVES





	<b>ULTRALIGHT L.S.T.™</b> FINE EDGE	46050	0-13658-46050-8	22-06050	0-13658-06050-0	Blade Length: 1.96" Overall Length: 4.62" Closed Length: 2.65" Weight: 0.6 oz Handle: Glass-filled Nylon
	<b>L.S.T.™</b> FINE EDGE	46009	0-13658-46009-6	22-06009	0-13658-06009-8	Blade Length: 2.63" Overall Length: 6.1" Closed Length: 3.61" Weight: 1.2 oz Handle: Glass-filled Nylon
	<b>SB™ 2.5</b> FINE EDGE	22-41535	0-13658-41535-5			Blade Length: 2.5" Overall Length: 5.8" Closed Length: 3.4" Weight: 1.6 oz Handle: Aluminum
	<b>STL™ 2.0</b> FINE EDGE	22-41122	0-13658-41122-7			Blade Length: 2.0" Overall Length: 5.0" Closed Length: 3.0" Weight: 1.0 oz Handle: Stainless Steel
	<b>STL™ 2.5</b> FINE EDGE	31-000716	0-13658-11980-2			Blade Length: 2.62" Overall Length: 6.0" Closed Length: 3.38" Weight: 1.5 oz Handle: Stainless Steel
	<b>3-BLADE STAG STOCKMAN™</b> FINE EDGE	22-41035	0-13658-41035-0			Blade Length: 2.75" [Longest] Blade Length: 1.88" [Second] Overall Length: 6.13" Closed Length: 3.38" Weight: 2.6 oz Handle: Genuine Stag
	<b>2.5 DOUBLE BOLSTER STAG™</b> FINE EDGE	22-41052	0-13658-41052-7	22-01052	0-13658-01052-9	Blade Length: 2.5" Overall Length: 6.17" Closed Length: 3.5" Weight: 2.6 oz Handle: Genuine Stag



# MULTI-TOOLS

## MINI/KEYCHAIN TOOLS



	CLAM	CLAM UPC	BOX	BOX UPC	SPECIFICATIONS	
	<b>ARTIFACT™</b> <b>BLACK</b>	22-41770	0-13658-41770-0		Overall Length: 4.8" Closed Length: 3.5" Weight: 1.5 oz  Stainless Steel Fine Edge Blade Phillips Driver Small & Medium Flat Drivers Bottle Opener Pry Bar Wire Stripper Lanyard Ring	
 <div data-bbox="451 698 546 755" style="background-color: black; color: white; padding: 2px;">7 TOOL MULTI-PLIERS</div>	<b>CURVE™</b> <b>BLUE</b>	31-000116	0-13658-11253-7		Overall Length: 3.5" Closed Length: 2.25" Weight: 1.0 oz	
	<b>GRAY</b>	31-000206	0-13658-11363-3		Saf.T.Plus™ Stainless Steel Fine Edge Knife Phillips Driver Small & Medium Flat Drivers Bottle Opener File Carabiner	
 <div data-bbox="451 1144 546 1201" style="background-color: black; color: white; padding: 2px;">10 TOOL MULTI-PLIERS</div>	<b>DIME™</b> <b>RED</b>	31-001040	0-13658-12406-6	30-000417	0-13658-12407-3	Overall Length: 4.25" Closed Length: 2.75" Weight: 2.2 oz  Stainless Steel Fine Edge Blade Spring Loaded Jaw Spring Loaded Needlenose Pliers Spring Loaded Scissors Retail Package Opener Wire Cutters File Medium Flat Driver Bottle Opener Tweezers

# MINI/KEYCHAIN TOOLS



CLAM

CLAM UPC

BOX

BOX UPC

SPECIFICATIONS

8 TOOL MULTI-PLIERS



**SHARD™**  
TITANIUM COATING

22-01769

0-13658-01769-6

Overall Length: 2.75"  
Weight: 0.6 oz

Stainless Steel  
Phillips Driver  
Small Flat Driver  
Medium Flat Driver  
Lanyard Ring  
Bottle Opener  
Pry Bar  
Wire Stripper

9 TOOL MULTI-PLIERS



**SPLICE™**  
BLACK

31-000013

0-13658-11155-4

Overall Length: 4.0"  
Closed Length: 2.4"  
Weight: 2.5 oz

Stainless Steel  
Scissors  
Fine Edge Knife  
Serrated Knife  
Phillips Driver  
Small Flat Driver  
Medium Driver  
Lanyard Ring  
Bottle Opener  
File

9 TOOL MULTI-PLIERS



**VISE™**  
BLACK

31-000021

0-13658-11172-1

Overall Length: 4.0"  
Closed Length: 2.4"  
Weight: 2.5 oz

Stainless Steel  
Needle Nose Pliers  
Fine Edge Knife  
Serrated Knife  
Phillips Driver  
Small Flat Driver  
Medium Driver  
Lanyard Ring  
Bottle Opener  
File

# POCKET/CLIP TOOLS



	CLAM	CLAM UPC	BOX	BOX UPC	SPECIFICATIONS
 <div data-bbox="451 341 541 397" style="background-color: black; color: white; padding: 2px; font-size: 8px; font-weight: bold;">12 TOOL MULTI- PLIERS</div> <div data-bbox="577 332 745 397" style="color: orange; font-weight: bold;">BALANCE™ GRAY</div>	31-001250	0-13658-12634-3	30-000508	0-13658-12757-9	Overall Length: 5.3" Closed Length: 3.8" Weight: 7.0 oz  Stainless Steel Needle Nose Pliers 1/2 Fine Edge & Serrated Blade Regular Pliers Tweezers Pinch Cut Wire Cutters Scissors Bottle Opener Interchangeable Medium Cross & Flat Head Drivers Interchangeable Small Cross & Flat Head Drivers
 <div data-bbox="451 755 541 812" style="background-color: black; color: white; padding: 2px; font-size: 8px; font-weight: bold;">9 TOOL MULTI- PLIERS</div> <div data-bbox="577 755 745 820" style="color: orange; font-weight: bold;">CRUCIAL™ GRAY</div>	31-001337	0-13658-12724-1	30-000016	0-13658-11153-0	Overall Length: 5.5" Closed Length: 3.6" Weight: 5.0 oz  Liner Lock Stainless Steel Needle Nose Pliers 1/2 Fine Edge & Serrated Blade Phillips Driver Large Flat Driver Bottle Opener V Cut Wire Cutters Carabineer Clip Pocket Clip Regular Pliers
 <div data-bbox="451 1177 541 1234" style="background-color: black; color: white; padding: 2px; font-size: 8px; font-weight: bold;">10 TOOL MULTI- PLIERS</div> <div data-bbox="577 1177 651 1242" style="color: orange; font-weight: bold;">FIT™ BLUE</div>	31-000731	0-13658-12000-6	30-000294	0-13658-11999-4	Overall Length: 8.5" Closed Length: 4.0" Weight: 5.1 oz  Saf.T.Plus™ Stainless Steel 25 Lumen L.E.D. Flashlight Tweezers Micro Flat Head Driver Micro Cross Driver 1/2 Fine Edge & Serrated Blade Scissors Interchangeable Large Cross & Flat Head Drivers Bottle Opener

25 Lumen L.E.D. Flashlight

# FULL SIZE TOOLS




CLAM CLAM UPC BOX BOX UPC

SPECIFICATIONS

12 TOOL MULTI-PLIERS

## EVO™ TOOL BLACK

22-41771 0-13658-41771-7



Overall Length: 6.0"  
 Closed Length: 3.93"  
 Weight: 9.3 oz

Saf.T.Plus™  
 Stainless Steel  
 Ballistic Nylon Sheath  
 Needle Nose Pliers  
 Fine Edge Blade  
 Serrated Edge Blade  
 Phillips Driver  
 Small Flat Driver  
 Medium Driver  
 Lanyard Ring  
 Bottle Opener & Can Opener  
 Wire Cutters  
 Scissors



12 TOOL MULTI-PLIERS

## MP 400 COMPACT SPORT

45500 0-13658-45500-9 05500 0-13658-05500-1



Overall Length: 5.63"  
 Closed Length: 4.37"  
 Weight: 6.8 oz

Saf.T.Plus™  
 Stainless Steel  
 Ballistic Nylon Sheath  
 Needle Nose Pliers  
 1/2 Fine Edge & Serrated Blade  
 Phillips Driver  
 Small Flat Driver  
 Medium Driver & Large Driver  
 Bottle Opener & Can Opener  
 Scissors  
 Wire Cutters & Wire Stripper



# FULL SIZE TOOLS









	CLAM	CLAM UPC	BOX	BOX UPC	SPECIFICATIONS
 <div data-bbox="451 324 546 381" style="background-color: black; color: white; padding: 2px; font-size: 8px;">13 TOOL MULTI- PLIERS</div>		<b>STRATA™</b>			 <p>Overall Length: 6.0" Closed Length: 4.0" Weight: 9.8 oz</p> <p>Saf.T.Plus™ Stainless Steel - E-Coat Ballistic Nylon Sheath Needle Nose Pliers 1/2 Fine Edge &amp; Serrated Blade Saw Phillips Driver Small Flat Driver &amp; Large Flat Driver Bottle Opener &amp; Can Opener Retail Package Opener File Tungsten Carbide Cutters Scissors</p>
 <div data-bbox="451 820 546 876" style="background-color: black; color: white; padding: 2px; font-size: 8px;">12 TOOL MULTI- PLIERS</div>		<b>SUSPENSION™</b>			 <p>Overall Length: 6.5" Closed Length: 4.0" Weight: 9.6 oz</p> <p>Saf.T.Plus™ Stainless Steel - Ti-Nitride Ballistic Nylon Sheath Needle Nose Pliers Fine Edge Blade Serrated Edge Blade Saw Phillips Driver Small &amp; Medium Flat Drivers Bottle Opener &amp; Can Opener V Cut Wire Cutters Scissors Lanyard Ring</p>

# GEAR

## LIGHTS



	CLAM	CLAM UPC	BOX	BOX UPC	SPECIFICATIONS
	<b>INFINITY ULTRA TASK LIGHT™</b> GREEN	22-80010	0-13658-80010-6	<input type="radio"/> WHITE LIGHT	Overall Length: 3.31" Weight: 2.2 oz Lumens: 8 Runtime: 32 hrs Batteries: [1] AA
	<b>IRIS™</b>	31-000063	0-13658-11196-7	<input type="radio"/> WHITE LIGHT	Overall Length: 6.375" Weight: 4.9 oz Lumens: 60 Runtime: 8 hrs Batteries: [2] AA
 	<b>OMNIVORE™</b>	22-80124	0-13658-80124-0	<input type="radio"/> WHITE LIGHT	Overall Length: 4.5" Weight: 4.0 oz Lumens: AA: 8, AAA: 9, CR123: 11 Runtime: 5 hrs Batteries: [1] AA, [1] AAA or [1] CR123
 	<b>OPTION™ 50</b>	22-80147	0-13658-80147-9	<input type="radio"/> WHITE LIGHT	Overall Length: 5.6" Weight: 4.6 oz Lumens: AA: 27, AAA: 17, CR123: 67 Runtime: AA: 12 hrs, AAA: 5 hrs, CR123: 3.25 hrs Batteries: [1] AA, [1] AAA or [1] CR123









**HIKING, BIKING, CAMPING, FISHING** – We have a knife or tool for every outdoor activity. When tested in the elements, Gerber's outdoor gear shows its true colors – sleek, sporty designs constructed with rugged materials. Deserts, Mountains, Forests – These are the ones to carry in the wild and open spaces.

**OUTDOOR**

# NEW FOR 2013



CLAM

CLAM UPC

BOX

BOX UPC

SPECIFICATIONS

NEW FOR 2013



## GATOR® BOLO MACHETE

31-002076 0-13658-13366-2

Overall Length:	22.5"
Blade Length:	15.5"
Weight:	20.8 oz
Weight with Sheath:	25.6 oz
Head:	1050 Steel
Sheath:	Ballistic Nylon
Handle:	Gator Grip®
Blade:	Full Tang

NEW FOR 2013



## GATOR® KUKRI

31-002074 0-13658-13364-8

Overall Length:	19"
Blade Length:	12"
Weight:	14.4 oz
Weight with sheath:	17.6 oz
Head:	1050 Steel
Sheath:	Ballistic Nylon
Handle:	Gator Grip®
Blade:	Full Tang

# KNIVES



## FIXED BLADE

		CLAM	CLAM UPC	BOX	BOX UPC	SPECIFICATIONS
	<b>BASIC™</b> SERRATED EDGE	31-000367	0-13658-11561-3			Blade Length: 3.4" Overall Length: 6.8" Weight: 3.77 oz Handle: TacHide™ Sheath: Molded Plastic Blade: Full Tang
	<b>BIG ROCK™ CAMP KNIFE</b> SERRATED EDGE	22-41588	0-13658-41588-1	22-01588	0-13658-01588-3	Blade Length: 4.5" Overall Length: 9.5" Weight: 6.4 oz Handle: TacHide™ Sheath: Ballistic Nylon Blade: Full Tang
	FINE EDGE			22-01589	0-13658-01589-0	
	<b>EPIC™</b> SERRATED EDGE	31-000368	0-13658-11564-4	30-000176	0-13658-11563-7	Blade Length: 3.45" Overall Length: 7.3" Weight: 5.12 oz Handle: Textured Glass-Filled Nylon Sheath: Molded Plastic Blade: Full Tang
	<b>GATOR™ FILLET - 6"</b> FINE EDGE	75230	0-13658-75230-6			Blade Length: 6.0" Overall Length: 11.14" Weight: 4.2 oz Handle: Gator Grip™ Sheath: Molded Plastic
	INCLUDES SHEATH WITH BUILT-IN SHARPENER					
	<b>GATOR™ FILLET - 7.5"</b> FINE EDGE	75231	0-13658-75231-3			Blade Length: 7.5" Overall Length: 12.2" Weight: 4.4 oz Handle: Gator Grip™ Sheath: Molded Plastic
	INCLUDES SHEATH WITH BUILT-IN SHARPENER					

## FOLDING CLIP



### **EZ-OUT™ RESCUE**

SERRATED EDGE

06971

0-13658-06971-8

Blade Length: 3.51"  
Overall Length: 7.95"  
Closed Length: 4.44"  
Weight: 2.4 oz  
Handle: Glass-filled Nylon with TacHide™

# MULTI-TOOLS



## MINI/KEYCHAIN TOOLS

CLAM

CLAM UPC

BOX

BOX UPC

SPECIFICATIONS



10 TOOL MULTI-PLIERS

**DIME™**  
**GREEN**

31-001132

0-13658-12551-3

30-000468

0-13658-12552-0

Overall Length: 4.25"  
Closed Length: 2.75"  
Weight: 2.2 oz

Stainless Steel  
Fine Edge Blade  
Spring Loaded Jaws  
Spring Loaded Needlenose Pliers  
Spring Loaded Scissors  
Retail Package Opener  
Wire Cutters  
File  
Medium Flat Driver  
Bottle Opener  
Tweezers

## POCKET/CLIP TOOLS



12 TOOL MULTI-PLIERS

**BALANCE™**  
**GREEN**

31-001248

0-13658-12635-0

30-000506



0-13658-12755-5

Overall Length: 5.3"  
Closed Length: 3.8"  
Weight: 7.0 oz

Stainless Steel  
Needle Nose Pliers  
1/2 Fine Edge & Serrated Blade  
Regular Pliers  
Tweezers  
Pinch Cut Wire Cutters  
Scissors  
Bottle Opener  
Interchangeable Medium Cross & Flat Head Drivers  
Interchangeable Small Cross & Flat Head Drivers


# POCKET/CLIP TOOLS





	CLAM	CLAM UPC	BOX	BOX UPC	SPECIFICATIONS
 <p><b>9</b> TOOL MULTI-PLIERS</p>					
					<p><b>CRUCIAL™</b> <b>GREEN</b></p>
	31-000238	0-13658-11416-6	30-000140	0-13658-11415-9	<p>Overall Length: 5.5"                      Closed Length: 3.6"                      Weight: 5.0 oz</p> <p>Liner Lock                      Stainless Steel                      Needle Nose Pliers                      1/2 Fine Edge &amp; Serrated Blade                      Phillips Driver                      Large Flat Driver                      Bottle Opener                      V Cut Wire Cutters                      Carabineer Clip                      Pocket Clip                      Regular Pliers</p>
 <p><b>8</b> TOOL MULTI-PLIERS</p> <p>ASSISTED OPENING</p>					
					<p><b>CRUCIAL F.A.S.T.™</b> <b>RED</b></p>
	31-000791	0-13658-12074-7	30-000315	0-13658-12075-4	<p>Overall Length: 5.8"                      Closed Length: 4.8"                      Weight: 5.8 oz</p> <p>Liner Lock                      Stainless Steel                      Needle Nose Pliers                      Assisted Opening 1/2 Fine Edge &amp; Serrated Blade                      Phillips Driver                      Long Large Flat Driver                      Bottle Opener                      V Cut Wire Cutters                      Carabineer Clip                      Pocket Clip                      Regular Pliers</p>
 <p><b>12</b> TOOL MULTI-PLIERS</p> <p>25 Lumen L.E.D. Flashlight</p>					
					<p><b>FIT™</b> <b>ORANGE</b></p>
	31-000919	0-13658-12249-9			<p>Overall Length: 8.5"                      Closed Length: 4.0"                      Weight: 5.1 oz</p> <p>Saf.T.Plus™                      Stainless Steel                      25 Lumen L.E.D. Flashlight                      1/2 Fine Edge &amp; Serrated Blade                      Micro Flat &amp; Cross Drivers                      Tweezers                      Pinch Curt Wire Cutters                      Scissors                      Interchangeable Large Cross &amp; Flat Head Drivers                      Bottle Opener</p>

## POCKET/CLIP TOOLS



	CLAM	CLAM UPC	BOX	BOX UPC	SPECIFICATIONS
 <div style="position: absolute; top: 10px; left: 10px; background-color: black; color: white; padding: 2px;">10 TOOL MULTI- PLIERS</div> <div style="position: absolute; bottom: 10px; left: 10px; border: 1px solid black; border-radius: 50%; padding: 2px; text-align: center;"> <small>SINGLE HAND OPERATION</small>  <b>SHOT</b>  <small>TECHNOLOGY</small> </div>					
	<b>OCTANE™</b> <b>RED</b>	31-000441	0-13658-11641-2		

## FULL SIZE TOOLS

 <div style="position: absolute; top: 10px; left: 10px; background-color: black; color: white; padding: 2px;">12 TOOL MULTI- PLIERS</div>	<b>STEADY™ TOOL</b>	31-001043	0-13658-12412-7	30-000419	0-13568-12413-4	Overall Length: 6" Closed Length: 4" Weight: 5.8 oz  Ballistic Nylon Sheath Smart Phone Suction Cup Attachment Compact Camera Screw Mount 2 Foldout Legs Create Tripod Fine Edge & Serrated Blade 3 Screwdriver Sizes Bottle Opener Pliers Wire Cutters Maximum Phone/ Camera Weight: 170 gm/340 gm
						

# GEAR

## AXES



	CLAM	CLAM UPC	BOX	BOX UPC	SPECIFICATIONS
					
<b>BACK PAXE II™</b>	31-000912	0-13658-12237-6			Overall Length: 8.98" Blade Length: 2.7" Weight: 19.4 oz Head: Forged Steel Sheath: Formed Plastic Handle: Fibercomp™
					
<b>SPORT™ AXE II</b>	31-000913	0-13658-12236-9			Overall Length: 14.2" Blade Length: 2.72" Weight: 21.4 oz Head: Forged Steel Sheath: Formed Plastic Handle: Fibercomp™
					
<b>CAMP AXE II</b>	31-000914	0-13658-12235-2			Overall Length: 17.52" Blade Length: 3.12" Weight: 38 oz Head: Forged Steel Sheath: Formed Plastic Handle: Fibercomp™
					
<b>EXTRA LARGE AXE</b>	31-000915	0-13658-12234-5			Overall Length: 28.43" Blade Length: 4.07" Weight: 49.8 oz Head: Forged Steel Sheath: Formed Plastic Handle: Fibercomp™
					
<b>SPLITTING AXE</b>	31-000917	0-13658-12240-6			Overall Length: 28.46" Blade Length: 3.38" Weight: 57.4 oz Head: Forged Steel Sheath: Formed Plastic Handle: Fibercomp™



# AXES



CLAM CLAM UPC BOX BOX UPC SPECIFICATIONS



**GATOR® COMBO AXE™ II  
WITH SAW**

31-001357 0-13658-12743-2



Overall Length: 15.6"  
Blade Length: 2.7"  
Weight: 26 oz  
Head: Forged Steel  
Sheath: Ballistic Nylon  
Handle: Gator Grip®



**GATOR® COMBO AXE™  
WITH KNIFE**

31-001054 0-13658-12449-3



Overall Length: 8.75"  
Blade Length: 2.7"  
Weight: 23.6 oz  
Head: Forged Steel  
Sheath: Ballistic Nylon  
Handle: Gator Grip®

# MACHETES

**GATOR® MACHETE JR**

31-000759 0-13658-12033-4



Overall Length: 18.75"  
Blade Length: 11.25"  
Weight: 14.3 oz  
Head: 1050 Steel  
Sheath: Ballistic Nylon  
Handle: Gator Grip®  
Blade: Full Tang

**GATOR® MACHETE**

31-000758 0-13658-12032-7



Overall Length: 25.7"  
Blade Length: 18"  
Weight: 18 oz  
Head: 1050 Steel  
Sheath: Ballistic Nylon  
Handle: Gator Grip®

# MACHETES



CLAM CLAM UPC BOX BOX UPC

SPECIFICATIONS



## GATOR® MACHETE PRO

31-000705 0-13658-12042-6

Overall Length: 16.5"  
 Blade Length: 10.5"  
 Weight: 17.9 oz  
 Head: 1050 Steel  
 Sheath: Ballistic Nylon  
 Handle: Gator Grip® Full Tang

## BRUSH THINNER

31-000083 0-13658-11225-4



Overall Length: 19.5"  
 Blade Length: 9"  
 Weight: 14.3 oz  
 Head: 1050 Steel  
 Sheath: Ballistic Nylon  
 Handle: Gator Grip®

# SAWS



## EXCHANGE-A-BLADE™ SAW 2 BLADE - COARSE (WOOD) & FINE (BONE)

46036 0-13658-46036-2

Overall Length: 14.21"  
 Closed Length: 8.11"  
 Blade Length: 6.18"  
 Weight: 7.8 oz  
 Blade Type: Coarse & Fine  
 Sheath: Ballistic Nylon  
 Handle: Glass Filled Nylon with Gator Grip® Inserts

# SAWS




CLAM

CLAM UPC

BOX

BOX UPC

SPECIFICATIONS



## EXCHANGE-A-BLADE™ SAW REPLACEMENTS

<b>COARSE (WOOD)</b>	70151	0-13658-70151-9	Blade Length:	6.2"
<b>FINE (BONE)</b>	70176	0-13658-70176-2	Weight:	1 oz



## SLIDING SAW™

22-41773	0-13658-41773-1	Overall Length:	14.75"
		Closed Length:	8.5"
		Blade Length:	6.5"
		Weight:	5 oz
		Blade Type:	Coarse (Wood)
		Sheath:	Ballistic Nylon
		Handle:	Glass Filled Nylon with Gator Grip® Inserts




## GATOR® SAW I

22-49472	0-13658-49472-5	Overall Length:	13.11"
		Weight:	24 oz
		Blade Length:	10"
		Blade Type:	Coarse & Fine
		Sheath:	Ballistic Nylon
		Handle:	Gator Grip®



## SAWS



CLAM CLAM UPC BOX BOX UPC

**GATOR® SAW III**  
**COARSE (WOOD), FINE (BONE) 20" COLLAPSIBLE CHAIN SAW**

22-41514 0-13658-41514-0

SPECIFICATIONS

Overall Length: 23.25  
 Weight: 32 oz  
 Blade Type: Coarse & Fine  
 Sheath: Ballistic Nylon  
 Handle: Gator Grip®

## SPADES



**E-TOOL™ WITH SERRATED BLADE**

30-000075 0-13658-11289-6

Overall Length: 23.8"  
 Closed Length: 9.37"  
 Weight: 40.6 oz

Glass-Filled Nylon Handle  
 Powder Coated Boron Carbon Steel  
 Spade  
 Anodized 7075 Aluminium Shaft

# SPADES



CLAM

CLAM UPC

BOX

BOX UPC

SPECIFICATIONS



## E-TOOL™ WITH SERRATED BLADE AND PICK

22-01945

0-13658-01945-4

Overall Length: 23.39"  
 Closed Length; 9.37"  
 Weight: 47.7 oz



Serrated Edge  
 Cast Pick Attachment  
 Glass-Filled Nylon Handle  
 Powder Coated Boron Carbon Steel Spade  
 Anodized Aluminium Shaft  
 Glass-Filled Nylon Handle  
 Molded Plastic Sheath



## GORGE™ FOLDING SHOVEL

22-41578

0-13658-41578-2

Overall Length: 16.5"  
 Closed Length; 9.25"  
 Weight: 28 oz



Easy-To-Use Push Button Slide Mechanism  
 Glass-Filled Nylon Handle  
 Pick Made for Hard Packed Ground  
 Hammer Feature for Pounding in Tent Stakes  
 Nylon Draw String Bag











**TOGETHER WITH BEAR GRYLLS,** Gerber makes survival tools for everyone from scouts on their first overnighter to seasoned adventurers exploring the backcountry. For survival in the elements, we created a line of the toughest, most innovative knives and tools available. With just your hands, your head and your tools you can account for everything needed to stay alive in the wild.

**SURVIVAL**

# NEW FOR 2013



NEW FOR 2013



## PARACORD FIXED BLADE™

FINE EDGE  
DROP POINT

CLAM	CLAM UPC	BOX	BOX UPC
31-001683	0-13658-13235-1		

### SPECIFICATIONS

Blade Length:	3.25"
Overall Length:	7.75"
Handle:	Paracord
Blade:	Full Tang

45 inches of paracord handle can be removed and used for survival tasks  
Reversible sheath  
Slim profile  
Lightweight  
Priorities of Survival Pocket Guide

NEW FOR 2013



## ULTIMATE PRO FIXED BLADE™

FINE EDGE  
DROP POINT

CLAM	CLAM UPC	BOX	BOX UPC
31-001901	0-13658-13268-9		

Blade Length:	4.8"
Overall Length:	10.0"
Weight:	13.7 oz
Handle:	TPE Overmold
Blade:	Full Tang 9Cr19Mov

Fire Starter  
Pommel  
Sharpener  
Whistle on Lanyard  
Sheath  
Priorities of Survival Pocket Guide

NEW FOR 2013



## ULTRA COMPACT FIXED BLADE™

FINE EDGE

CLAM	CLAM UPC	BOX	BOX UPC
31-001516	0-13658-12985-6		

Blade Length:	3.25"
Overall Length:	6.25"
Weight:	4.5 oz
Blade:	Full Tang

Lightweight, molded locking sheath  
Removeable Clip  
Multiple Lashing Holes for Paracord  
Slots to accommodate 3/4" webbing  
Straps to Boot  
Clips to Belt  
Hang around Neck on length of paracord  
Priorities of Survival Pocket Guide

NEW FOR 2013



## GRANDFATHER KNIFE™

CLAM	CLAM UPC	BOX	BOX UPC
31-002181	0-13658-13483-6		

Blade Length:	2.75"
Overall Length:	6.5"
Closed Length:	3.75"
Weight:	3.5 oz
Handle:	Overmolded TPU Rubber w/stainless steel

Fine Edge Blade  
Flat Driver, Phillips Driver  
Cork Screw  
Bottle Opener  
File  
Lanyard Ring  
Priorities of Survival Pocket Guide

# NEW FOR 2013



NEW FOR 2013



## INTENSE TORCH™

CLAM	CLAM UPC	BOX	BOX UPC
31-001794	0-13658-13180-4		

### SPECIFICATIONS

Overall Length:	5.98"
Weight:	3.89 oz
Batteries:	AA[2]

110 Lumens  
 Durable anodized aluminum body  
 Tri-sided No-Roll on Flat Surfaces  
 Waterproof (IPX8)  
 Momentary on push button for signaling.  
 Priorities of Survival Pocket Guide

NEW FOR 2013



## RECHARGEABLE TORCH™

31-001796	0-13658-13182-8
-----------	-----------------

Overall Length:	6.25"
Batteries:	Rechargeable

80 lumens  
 Crank powered light  
 Recharge by Spinning End  
 Never Run out of batteries  
 Durable anodized aluminum body  
 Priorities of Survival Pocket Guide

NEW FOR 2013



## SURVIVAL BELT™

31-001771	0-13658-13178-1
-----------	-----------------

Overall Length:	48"
-----------------	-----

Heavy Nylon Webbing  
 Hidden compartment in buckle houses:  
 - Fishing Line, Hooks & Weights  
 - Snare Wire  
 - Signaling mirror  
 Rear of buckle, removable mini screwdriver with flat and philips  
 removable bottle opener  
 Priorities of Survival Pocket Guide

NEW FOR 2013



## SURVIVAL BLANKET™

31-001785	0-13658-13196-5
-----------	-----------------

Overall Length:	96" x 30"
Thickness:	12 Microns

Lightweight, compact blanket for warmth or as a heat shield  
 Made of Durable, Tear Resistant Material (Low Density Polyethylene)  
 Features the priorities of survival printed on surface  
 Packaged in re-usable bag

# NEW FOR 2013



NEW FOR 2013



## SURVIVAL BRACELET™

CLAM 31-001773 CLAM UPC 0-13658-13186-6 BOX BOX UPC

SPECIFICATIONS Overall Length: 11.5"

Paracord to be used in Survival Emergency  
Easy, one-hand size adjustment  
Whistle  
One size fits most  
12' of Paracord  
Priorities of Survival Pocket Guide

NEW FOR 2013



## COMPACT COMPASS™

31-001777 0-13658-13188-0

Overall Length: 2.28"

Compass with convenient zipper pull  
Durable plastic body  
Compact size makes it easy to take everywhere  
Priorities of Survival Pocket Guide

NEW FOR 2013



## SURVIVAL LANYARD™

31-001788 0-13658-13198-9

Overall Length: 5"

Paracord can be unwound and used for other tasks  
Emergency whistle  
Easily attaches to packs, keychain, etc.  
6' of Paracord  
Priorities of Survival Pocket Guide

NEW FOR 2013



## SURVIVAL PONCHO™

31-001790 0-13658-13192-7

Approx Dimensions: 40" x 21"  
Lightweight protection from wet weather  
Hooded  
Doubles as rescue marker (flag)  
Priorities of Survival Pocket Guide  
Material: Polyethylene  
Packaged in re-useable bag

NEW FOR 2013



## SURVIVAL HATCHET™

31-002070 0-13658-13383-9

Blade Length: 3.5"  
Overall Length: 9.46"  
Weight: 20.8 oz  
Handle: Nylon  
Blade: 5CR13



Full Tang Construction  
Grippy Rubber Handle  
Priorities of Survival Pocket Guide

NEW FOR 2013



## COMPACT PARANG™

31-002072 0-13658-13361-7

Overall Length: 15.08"  
Blade Length: 19.34"  
Weight in Sheath: 13.6 oz



Angled Blade  
High Carbon Steel Blade  
Full Tang Construction  
Ergonomic Textured Rubber Grip  
Lanyard Cord  
Nylon Sheath  
Ballistic Nylon Sheath  
Priorities of Survival Pocket Guide

# KNIVES



## FIXED BLADE

CLAM

CLAM UPC

BOX

BOX UPC

SPECIFICATIONS



### COMPACT FIXED BLADE™

FINE EDGE  
DROP POINT

31-001066

0-13658-12444-8

Blade Length: 3.4"  
Overall Length: 7.8"  
Weight: 3.77 oz  
Handle: Durable Rubber  
Blade: Full Tang

Ergonomic  
Lightweight Plastic Sheath  
Sheath Clips to Belt/Backpack  
Priorities of Survival Pocket Guide



### ULTIMATE KNIFE™

SERRATED EDGE  
DROP POINT

31-000751

0-13658-12023-5

Blade Length: 4.8"  
Overall Length: 10.0"  
Weight: 11.2 oz  
Handle: Textured Rubber Grip  
Blade: Full Tang

Fire Starter  
Sharpener in Sheath  
Whistle on Lanyard  
Ballistic Nylon Sheath  
Priorities of Survival Pocket Guide



### ULTIMATE KNIFE™

FINE EDGE  
DROP POINT

31-001063


0-13658-12440-0

Blade Length: 4.8"  
Overall Length: 10.0"  
Weight: 11.2 oz  
Handle: Textured Rubber Grip


Fire Starter  
Sharpener in Sheath  
Whistle on Lanyard  
Ballistic Nylon Sheath  
Priorities of Survival Pocket Guide

## FOLDING SHEATH




	CLAM	CLAM UPC	BOX	BOX UPC	SPECIFICATIONS
 <p><b>FOLDING SHEATH KNIFE™</b> SERRATED EDGE DROP POINT</p>	31-000752	0-13658-12024-2			<p>Blade Length: 3.6" Overall Length: 8.5" Closed Length: 4.9" Weight: 4.3 oz Weight with Sheath: 5.3 oz Handle: Textured Rubber Grip</p> <p>1/2 Serrated Stainless Steel Dual-Sided Thumb Stud Ergonomic Textured Rubber Grip Lock Back Lightweight, Military-Grade Nylon Sheath Sheath horizontal or vertical mount Priorities of Survival Pocket Guide</p>

## FOLDING CLIP

 <p><b>SCOUT™</b> SERRATED EDGE DROP POINT</p>	31-000754	0-13658-12029-7			<p>Blade Length: 3.3" Overall Length: 7.3" Closed Length: 4.0" Weight: 2.4 oz Handle: Textured Rubber Grip</p> <p>Thin and Lightweight 1/2 Serrated Stainless Steel Dual-Sided Thumb Stud Ergonomic Textured Rubber Grip Lock Back Clip for Pocket Carry Priorities of Survival Pocket Guide</p>
--	-----------	-----------------	--	--	--

## FOLDING SINGLE BLADE

 <p><b>COMPACT SCOUT™</b> SERRATED EDGE DROP POINT</p>	31-000760	0-13658-12035-8			<p>Blade Length: 2.5" Overall Length: 5.8" Closed Length: 3.3" Weight: 4.8 oz Handle: Textured Rubber Grip</p> <p>1/2 Serrated Stainless Steel Thin and Lightweight Nail Nick in Blade Lock Back Oversized Finger Notch Priorities of Survival Pocket Guide</p>
--	-----------	-----------------	--	--	---

# MULTI-TOOLS



## MINI/KEYCHAIN TOOLS

CLAM

CLAM UPC

BOX

BOX UPC

SPECIFICATIONS

10  
TOOL  
MULTI-  
PLIERS

### COMPACT MULTI-TOOL™

31-000750

0-13658-12018-1

Open Length: 4.3"  
Closed Length: 2.5"  
Weight: 3.0 oz

Needle Nose Pliers  
Wire Cutters  
Fine Edge Knife  
Serrated Knife  
Phillips Screwdriver  
Small Flat Driver  
Medium Flat Driver  
Lanyard Ring  
Bottle Opener  
Tweezers  
Priorities of Survival Pocket Guide



## MID-SIZE/POCKET TOOLS

5  
TOOL  
MULTI-  
PLIERS

### POCKET TOOL™

31-001050

0-13658-12423-3

Open Length: 5.5"  
Closed Length: 3.2"  
Weight: 2.9 oz  
5CR15Mov

Tough, Rubberized Handle  
All Basic Tools  
5 Components  
Fine Edge Blade  
Bottle Opener  
Philips head driver  
Small & Medium Size  
Flat Driver  
Priorities of Survival Pocket Guide





# FULL SIZE TOOLS



CLAM

CLAM UPC

BOX

BOX UPC

SPECIFICATIONS

12 TOOL MULTI-PLIERS

## SURVIVAL TOOL PACK



Open Length: 6.0"  
 Closed Length: 4.0"  
 Weight: 11.14 oz

- Locking Case
- Attaches to Belt / Backpack Strap
- 12 Components
- Needle Nose Pliers
- Standard Pliers
- File
- Wire Cutters
- Partially Serrated Blade
- Wood Saw
- Small Flathead Driver
- Bottle Open
- Scissors
- Crosshead Driver
- Pierce
- Medium Flathead
- Flashlight
- Firestarter Rod
- Priorities of Survival Pocket Guide

12 TOOL MULTI-PLIERS

## ULTIMATE MULTI-TOOL™

31-000749

0-13658-12019-8



Overall Length: 6.3"  
 Closed Length: 4.0"  
 Weight: 8.8 oz

- Needle Nose Pliers
- Fine Edge Knife
- Serrated Knife
- Saw
- Phillips Screwdriver
- Small Flat Driver
- Medium Flat Driver
- Lanyard Ring
- Bottle Opener
- Scissors
- Wire Cutters
- Ergonomic Textured Rubber Grip
- Spring Loaded Jaw
- External Components
- Saf.T.Plus™
- Nylon Sheath with Land to Air Rescue Instructions
- Priorities of Survival Pocket Guide

# GEAR

## LIGHTS



CLAM CLAM UPC BOX BOX UPC SPECIFICATIONS

### HANDS-FREE TORCH™



31-001028 0-13658-12385-4

Overall Length: 2.45"  
 Overall Width: 1.31"  
 Weight: 3.89 oz  
 Lumens/Runtime:  
 High: 25/8.75 hrs  
 Low: 8/15 hrs  
 Batteries: [1] AAA

Hands Free  
 Headband Stows Extra Battery  
 Adjustable Lamp - High, Low & Off  
 Priorities of Survival Pocket Guide

### MICRO TORCH™



31-001034 0-13658-12393-9

Overall Length: 1.78"  
 Weight: .28 oz  
 Lumens/Runtime:  
 High: 8/3.5 hrs  
 Low: 3/9hrs  
 Beacon/Blinking: 8/6 hrs  
 Batteries: [2] CR1616

Compact  
 Long Lasting L.E.D. Bulb  
 4 Settings - High, Low,  
 Beacon/Blinking & Off  
 Easy to Use Soft Rubber Switch  
 Priorities of Survival Pocket Guide

### SURVIVAL TORCH™



31-001031 0-13658-12389-2

Overall Length: 5.98"  
 Weight: 3.89 oz  
 Lumens/Runtime:  
 High: 15/36 hrs  
 Batteries: [1] AA

Water Resistant  
 Compact  
 Storage Compartment holds Matches  
 & Tinder  
 Priorities of Survival Pocket Guide

# CANTEENS



CLAM

CLAM UPC

BOX

BOX UPC

SPECIFICATIONS

## CANTEEN/CUP™

31-0001062

0-13658-12450-9

Size: 10" x 6" x 3"  
Weight: 12.5 oz



*In sheath*

- Food Grade Aluminum Cup
- BPA-Free Water Bottle
- Snug Nylon Sheath
- Textured Exterior
- Leak-Proof Lock Top
- 1 Liter Capacity
- Priorities of Survival Pocket Guide

# FIRE STARTERS



## FIRE STARTER™

31-000699

0-13658-12021-1

Overall Length: 4.8"  
Weight: 2.6 oz

- Compact
- Ferrocium Rod and Metal Striker
- Lanyard
- Emergency Whistle
- Waterproof Tinder Storage
- Land to Air Rescue and SOS
- Instructions
- Priorities of Survival Pocket Guide

# KITS



## BASIC KIT™

CLAM	CLAM UPC	BOX	BOX UPC
31-000700	0-13658-12022-8		

### SPECIFICATIONS

Sheath Dimensions: 4.5" x 5"  
 Kit Weight: 4.2 oz

Lightweight, Waterproof Bag  
 First Aid Kit  
 Gerber® Mini-Paraframe™ Knife  
 Emergency Whistle  
 Fire Starter  
 Waterproof Matches  
 Snare Wire  
 Emergency Cord  
 Cotton Ball -Fire Tinder  
 Land to Air Rescue & SOS Instructions  
 Priorities of Survival Pocket Guide



## SCOUT ESSENTIALS KIT™

31-001078	0-13658-12453-0
-----------	-----------------

Overall Size: 4.75" x 3.75" x 1"  
 Weight: 5.4 oz

Polypropylene Case  
 First Aid Kit  
 Waterproof Matches  
 L.E.D. Micro Torch Light  
 Compact Scout Knife  
 Button Compass  
 Priorities of Survival Pocket Guide



## ULTIMATE KIT™

31-000701	0-13658-12025-9
-----------	-----------------



Sheath Dimensions: 4.5" x 6.8"  
 Kit Weight: 9.4 oz

Lightweight, Waterproof Bag  
 Gerber® Miniature Multi-tool:  
*Needle Nose Pliers*  
*Wire Cutters*  
*Fine Edge Knife*  
*Phillips Screwdriver*  
*Small & Medium Flat Driver*  
*Lanyard Ring*  
*Bottle Opener*  
*Tweezers*


Survival Blanket  
 Snare Wire  
 Emergency Cord  
 Waxed Thread  
 Fishing Kit  
 Sewing kit  
 Hand Saw  
 Signaling Mirror  
 Fire Starter  
 Waterproof matches  
 Cotton Ball - Fire Tinder  
 Miniature Light  
 Land to Air Rescue & SOS Instructions  
 Priorities of Survival Pocket Guide

# MACHETES




	CLAM	CLAM UPC	BOX	BOX UPC	SPECIFICATIONS
 <p><b>PARANG™</b></p>	31-002298	0-13658-13656-4			Overall Length: 19.5" Blade Length: 13.5" Weight: 19.4 oz Weight in Sheath: 25.4 oz
					Angled Blade High Carbon Steel Blade Full Tang Construction Ergonomic Textured Rubber Grip Lanyard Cord Nylon Sheath Ballistic Nylon Sheath Priorities of Survival Pocket Guide

# SAWS

 <p><b>SLIDING SAW™</b></p>	31-001058	0-13658-12434-9			Overall Length: 14.75" Closed Length: 8.5" Weight: 5 oz
					For Small Brush, Branches & Limbs Cross Cut Teeth Rubberized Handle Locking Retractable 6" Blade Priorities of Survival Pocket Guide

# SHARPENERS

 <p><b>FIELD SHARPENER</b></p>	31-001270	0-13658-12653-4			Overall Length: 4.5" Total Weight: 2.3 oz
					Hard Plastic Cover Pocket Size Grippy Handle Sharpens Fine Edge & Serrated Blades Coarse Carbide Insert Fine Ceramic Insert Priorities of Survival Pocket Guide









**WE MAKE KNIVES, TOOLS AND GEAR** for every type of hunting. From small game to trophy quarry, Gerber products can handle every situation. Designed to be all-around tough at the camp and on the hunt, we make hunting specific gear with long-lasting blades, tactile handles and all-weather sheaths. Gerber knives, tools and gear hunt just as hard as you do.

**HUNTING**





# MYTH™ SERIES

## FIXED BLADE KNIVES




		CLAM	CLAM UPC	BOX	BOX UPC	SPECIFICATIONS
	<b>MYTH™ COMPACT FIXED BLADE</b> FINE EDGE	31-001156	0-13658-12570-4			Blade Length: 3.25" Overall Length: 7.25" Weight: 1.0 oz Sheath: Integrated Sharpener Handle: Textured Rubber
	<b>MYTH™ E-Z OPEN</b> FINE EDGE	31-001168	0-13658-12582-7			Blade Length: 3.5" Overall Length: 9.0" Weight: 2.6 oz Sheath: Integrated Sharpener Handle: Textured Rubber
	<b>MYTH™ FIXED BLADE PRO [DROP POINT]</b> FINE EDGE	31-001092	0-13658-12471-4			Blade Length: 3.75" Overall Length: 8.5" Weight: 4.7 oz Sheath: Integrated Sharpener Handle: Textured Rubber
	<b>MYTH™ FIXED BLADE PRO [GUT HOOK]</b> FINE EDGE	31-001095	0-13658-12477-6			Blade Length: 3.75" Overall Length: 8.5" Weight: 4.9 oz Sheath: Integrated Sharpener Handle: Textured Rubber

## FOLDING SHEATH KNIVES

	<b>MYTH™ FOLDER [DROP POINT]</b> FINE EDGE	31-001164	0-13658-12578-0			Blade Length: 3.5" Overall Length: 8.25" Closed Length: 4.75" Weight: 3.1 oz Sheath: Ingrated Sharpener Handle: Textured Rubber
	<b>MYTH™ FOLDER [GUT HOOK]</b> FINE EDGE	31-001160	0-13658-12574-2			Blade Length: 3.5" Overall Length: 8.25" Closed Length: 4.75" Weight: 3.0 oz Sheath: Ingrated Sharpener Handle: Textured Rubber

## FOLDING CLIP KNIVES

	<b>MYTH™ POCKET FOLDER</b> FINE EDGE	31-001088	0-13658-12464-6			Blade Length: 3.0" Overall Length: 7.25" Closed Length: 4.25" Weight: 2.7 oz Handle: Textured Rubber
---	---	-----------	-----------------	--	--	--

# MYTH™ SERIES

## KITS



CLAM

CLAM UPC

BOX

BOX UPC

SPECIFICATIONS



### MYTH™ FIELD DRESS KIT

FINE EDGE  
GUT HOOK/  
SMALL FIXED BLADE

31-001159

0-13658-12573-5



**Gut Hook :**  
Blade Length: 3.75"  
Overall Length: 8.5"  
Weight: 4.9 oz  
**Small Fixed Blade:**  
Blade Length: 3.25"  
Overall Length: 7.25"  
Weight: 1.0 oz  
Sheath: Integrated Sharpener  
Handle: Textured Rubber

## SAWS



### MYTH™ FOLDING SAW

31-001167

0-13658-12581-0

Overall Length: 15.5"  
Closed Length: 8.5"  
Blade Length: 6.75"  
Weight: 8.3 oz  
Handle: Textured Rubber

Stainless Steel Saw Blade  
Fine/Bone Saw Blade  
Push Button Locking/Closing  
Mechanisms  
Lanyard Hole

## SHARPENERS



### MYTH™ FIELD SHARPENER

31-001526

0-13658-13001-2

Overall Length: 7.0"  
Closed Length: 4.0"  
Weight: 2.4 oz

## LIGHTS



### MYTH™ HANDS FREE LIGHT





WHITE  
LIGHT

Weight: 1.4 oz  
Lumens: 25  
Runtime: 5 hrs  
Batteries: [1] AAA

# GATOR™ SERIES

## FIXED BLADE KNIVES



	CLAM	CLAM UPC	BOX	BOX UPC	SPECIFICATIONS
 <p><b>GATOR™ FIXED</b> FINE EDGE DROP POINT</p>	46904	0-13658-46904-4	06904	0-13658-06904-6	Blade Length: 4.5" Overall Length: 9.5" Weight: 5.4 oz Sheath: Lined Ballistic Nylon Handle: Gator Grip™
 <p><b>GATOR™ FIXED</b> FINE EDGE GUT HOOK</p>	46906	0-13658-46906-8	06906	0-13658-06906-0	Blade Length: 4.5" Overall Length: 9.5" Weight: 5.4 oz Sheath: Lined Ballistic Nylon Handle: Gator Grip™

## FOLDING SHEATH KNIVES

 <p><b>GATOR™</b> FINE EDGE 154CM</p>			06064	0-13658-06064-7	Blade Length: 3.76" Overall Length: 8.58" Closed Length: 4.96" Weight: 5.4 oz Sheath: Ballistic Nylon Handle: Gator Grip™
 <p><b>GATOR™</b> SERRATED EDGE CLIP POINT FINE EDGE CLIP POINT</p>	46079	0-13658-46079-9	06079	0-13658-06079-1	Blade Length: 3.76" Overall Length: 8.58" Closed Length: 4.96" Weight: 5.4 oz Sheath: Ballistic Nylon Handle: Gator Grip™
	46069	0-13658-46069-0	06069	0-13658-06069-2	
 <p><b>GATOR™</b> FINE EDGE GUT HOOK</p>	46932	0-13658-46932-7	06932	0-13658-06932-9	Blade Length: 3.76" Overall Length: 8.58" Closed Length: 4.96" Weight: 5.4 oz Sheath: Ballistic Nylon Handle: Gator Grip™
 <p><b>GATOR™ II</b> FINE EDGE GUT HOOK</p>	22-41415	0-13658-41415-0			Blade Length: 3.7" Overall Length: 8.58" Closed Length: 4.72" Weight: 4.4 oz Sheath: Ballistic Nylon Handle: Gator Grip™


# GATOR™ SERIES



## FOLDING SHEATH KNIVES



	CLAM	CLAM UPC	BOX	BOX UPC	SPECIFICATIONS
 <p><b>GATOR™ II WITH E-Z GUT HOOK</b> SERRATED EDGE</p> 	22-41417	0-13658-41417-4			Blade Length: 3.62" Overall Length: 8.58" Closed Length: 4.72" Weight: 4.4 oz Sheath: Ballistic Nylon Handle: Gator Grip™
 <p><b>GATORMATE™</b> FINE EDGE CLIP POINT</p>			06149	0-13658-06149-1	Blade Length: 3.08" Overall Length: 7.2" Closed Length: 4.14" Weight: 3.0 oz Sheath: Ballistic Nylon Handle: Gator Grip™

### AXES

 <p><b>GATOR® COMBO AXE™ II</b> WITH SAW</p>	22-41420	0-13658-41420-4			Overall Length: 15.6" Blade Length: 2.7" Weight: 26 oz Head: Forged Steel Sheath: Ballistic Nylon Handle: Gator Grip®
---	----------	-----------------	--	--	--

 <p><b>GATOR® COMBO AXE™</b> WITH KNIFE</p>	31-001854	0-13658-13167-5			Overall Length: 8.75" Blade Length: 2.7" Weight: 23.6 oz Head: Forged Steel Sheath: Ballistic Nylon Handle: Gator Grip®
--	-----------	-----------------	--	---	--



### SAWS

 <p><b>GATOR® EXCHANGE-A-BLADE™ SAW</b></p>	22-41457	0-13658-41457-0			
---	----------	-----------------	--	--	--

# FREEMAN™ SERIES

## FIXED BLADE KNIVES



		CLAM	CLAM UPC	BOX	BOX UPC	SPECIFICATIONS
	<b>FREEMAN™ GUIDE</b> FINE EDGE DROP POINT	31-000588	0-13658-11831-7			Blade Length: 4.0" Overall Length: 8.38" Weight: 4.4 oz Sheath: Lined Ballistic Nylon Handle: TacHide™
	<b>FREEMAN™ GUIDE</b> FINE EDGE GUT HOOK	31-000589	0-13658-11832-4			Blade Length: 4.0" Overall Length: 8.38" Weight: 4.4 oz Sheath: Lined Ballistic Nylon Handle: TacHide™

## FOLDING SHEATH KNIVES

	<b>FREEMAN™ GUIDE FOLDER</b> FINE EDGE DROP POINT	31-000591	0-13658-11834-8			Blade Length: 3.62" Overall Length: 8.12" Closed Length: 4.5" Weight: 6.6 oz Sheath: Ballistic Nylon Handle: TacHide™
	<b>FREEMAN™ GUIDE FOLDER</b> FINE EDGE GUT HOOK	31-000592	0-13658-11835-5			Blade Length: 3.62" Overall Length: 8.12" Closed Length: 4.5" Weight: 6.6 oz Sheath: Ballistic Nylon Handle: TacHide™

# PROFILE™ SERIES

## FIXED BLADE KNIVES



CLAM CLAM UPC BOX BOX UPC

SPECIFICATIONS



**PROFILE™**  
FINE EDGE  
DROP POINT

22-41795 0-13658-41795-3



**PROFILE™**  
FINE EDGE  
GUT HOOK

22-41131 0-13658-41131-9

Blade Length: 4.0"  
Overall Length: 8.56"  
Weight: 6.1 oz  
Sheath: Ballistic Nylon  
Handle: TacHide™

## FOLDING SHEATH KNIVES



**PROFILE™**  
FINE EDGE

22-41297 0-13658-41297-2 22-01297 0-13658-01297-4

Blade Length: 3.5"  
Overall Length: 8.5"  
Closed Length: 4.75"  
Weight: 4.3 oz  
Sheath: Ballistic Nylon  
Handle: TacHide™



**PROFILE™**  
FINE EDGE - GUT HOOK

22-41708 0-13658-41708-3

Blade Length: 3.5"  
Overall Length: 8.5"  
Closed Length: 4.75"  
Weight: 4.3 oz  
Sheath: Ballistic Nylon  
Handle: TacHide™

# GEAR

## FIXED BLADE KNIVES



CLAM CLAM UPC BOX BOX UPC SPECIFICATIONS



### E-Z SKINNER™

22-48398 0-13658-48398-9



Blade Length: 5.39"  
Overall Length: 2.56"  
Weight: 4.4 oz  
Sheath: Ballistic Nylon



### E-Z ZIP™

45924 0-13658-45924-3



Overall Length: 5.0"  
Weight: 2.4 oz  
Sheath: Ballistic Nylon

## FOLDING CLIP KNIFE



### METOLIUS™ POCKET FOLDER

FINE EDGE

31-000586 0-13658-11828-7

Blade Length: 3.0"  
Overall Length: 7.0"  
Closed Length: 4.0"  
Weight: 4.7 oz  
Handle: TacHide™

## SHEARS




### TAKE-A-PART™ GAME SHEARS

46001 0-13658-46001-0

Overall Length: 8.03"  
Weight: 16 oz  
Sheath: Ballistic Nylon



# SAWS



**E-Z SAW™**

CLAM	CLAM UPC	BOX	BOX UPC
22-48397	0-13658-48397-2		

SPECIFICATIONS	
Blade Length:	3.58"
Overall Length:	5.75"
Weight:	2.2 oz
Sheath:	Ballistic Nylon



**E-Z SAW™ II**

CLAM	CLAM UPC	BOX	BOX UPC
22-41140	0-13658-41140-1		

Blade Length:	5.25"
Overall Length:	7.5"
Weight:	2.8 oz
Sheath:	Ballistic Nylon

# SHARPENERS



*Closed*

**DF6™ COMPACT SHARPENER**

CLAM	CLAM UPC	BOX	BOX UPC
22-41846	0-13658-41846-2		

Overall Length:	3.0"
Weight:	3.1 oz



*Closed*

**DF8™ SHARPENER**

CLAM	CLAM UPC	BOX	BOX UPC
22-41847	0-13658-41847-9		

Overall Length:	3.25"
Weight:	6.2 oz



*Closed*

**DIAMOND KNIFE SHARPENER**

CLAM	CLAM UPC	BOX	BOX UPC
09841	0-13658-09841-1		

Overall Length:	7.4"
Closed Length:	5.35"
Weight:	1.6 oz





**IN THE HANDS OF FIRST RESPONDERS AND MILITARY PERSONNEL**, the proper tool can be the difference between life and death. Gerber's tactical line was created with this in mind. Every single tool is built for a specific purpose to make the job of firefighters, soldiers, police officers and EMTs easier and more effective. We make tools that save lives.

**TACTICAL**

# NEW FOR 2013



NEW FOR 2013



## BREACH™ WEAPONS LIGHT

○ WHITE LIGHT

CLAM

CLAM UPC

BOX

BOX UPC

SPECIFICATIONS

30-000713

0-13658-13677-9

Overall Length: 5.625"  
Weight: 5.6 oz  
Lumens: ~230  
Runtime: ~2.5 hrs  
Batteries: [2] CR123

NEW FOR 2013

8 TOOL MULTI-PLIERS



## BULLRUSH™ BLACK

31-001749

0-13658-13095-1

30-000663

0-13658-13275-7

Overall Length: 5.8"  
Closed Length: 3.6"  
Weight: 8.32 oz

Full-Size Plier Jaws  
G-10 Handles  
Fine Edge Blade  
Serrated Edge Blade  
Strap Cutter  
Flat Head Driver  
Large Phillips Head Driver  
Pinch Wire Cutters

NEW FOR 2013



## EVO™ LARGE - TANTO

SERRATED EDGE  
TANTO

31-001755

0-13658-13101-9

30-000656

0-13658-13266-5

Blade Length: 3.5"  
Overall Length: 8.25"  
Closed Length: 4.63"  
Weight: 3.0 oz  
Handle: AL 6061-T6

NEW FOR 2013



## IMPROMPTU TACTICAL PEN™

31-001880

13658-13210-8

Overall Length: 5.59"  
Diameter: .5"  
Weight: 1.02 oz

Machined Aluminum Body  
Stainless Steel Pocket Clip  
Carbide Glass-Breaker Tip  
"Rite in the Rain" Ink Cartridge  
Black Anodized

# NEW FOR 2013



			CLAM	CLAM UPC	BOX	BOX UPC	SPECIFICATIONS	
			<b>MINI F.A.S.T. DRAW™ - TANTO</b> SERRATED EDGE TANTO	31-001753	0-13658-13098-2	30-000655	0-13658-13265-8	Blade Length: 2.13" Overall Length: 5.0" Closed Length: 3.0" Weight: 1.75 oz Handle: Textured Nylon
			<b>F.A.S.T. DRAW™ - TANTO</b> SERRATED EDGE TANTO	31-001751	0-13658-13097-5	30-000654	0-13658-13264-1	Blade Length: 3.0" Overall Length: 7.25" Closed Length: 4.25" Weight: 3.5 oz Handle: Textured Nylon
			<b>MINI PARAFRAME™ - TANTO</b> FINE EDGE TANTO	31-001729	0-13658-13071-5	30-000651	0-13658-13262-7	Blade Length: 2.13" Overall Length: 5.25" Closed Length: 3.13" Weight: 1.5 oz Handle: Steel
			<b>PARAFRAME™ - TANTO</b> SERRATED EDGE TANTO	31-001731	0-13658-13074-6	30-000652	0-13658-13263-4	Blade Length: 2.88" Overall Length: 7.0" Closed Length: 4.13" Weight: 2.9 oz Handle: Steel
			<b>PARAFRAME™ II - TANTO</b> SERRATED EDGE TANTO	31-001734	0-13658-13080-7	30-000653	0-13658-13296-2	Blade Length: 3.5" Overall Length: 8.13" Closed Length: 4.75" Weight: 4.3 oz Handle: Steel
			<b>PROPEL™ AO</b> SERRATED EDGE TANTO			30-000698	0-13658-13410-2	Blade Length: 3.5" Overall Length: 8.5" Closed Length: 3.5" Weight: 4.28 oz Handle: G-10 Blade Steel: 420 HC

# NEW FOR 2013













		CLAM	CLAM UPC	BOX	BOX UPC	SPECIFICATIONS	
	 	<b>PROPEL™ AUTO</b> SERRATED EDGE TANTO <i>Automatic knives available through authorized dealers only.</i>		30-000718	0-13658-13372-3	Blade Length: 3.51" Overall Length: 8.52" Closed Length: 5" Weight: 4.28 oz Handle: G-10 Blade Steel: 420 HC	
	  	<b>PROPEL DOWNRANGE™ AO</b> SERRATED EDGE TANTO		30-000725	0-13658-13411-9	Blade Length: 3.5" Overall Length: 8.5" Closed Length: 5.0" Weight: 4.28 oz Handle: G-10 Blade Steel: S30V	
	 	<b>PROPEL DOWNRANGE™ AUTO</b> SERRATED EDGE TANTO <i>Automatic knives available through authorized dealers only.</i>		30-000695	0-13658-13482-9	Blade Length: 3.5" Overall Length: 8.52" Closed Length: 5.0" Weight: 4.28 oz Handle: G-10 Blade Steel: S30V	
	 	<b>MINI SWAGGER™ AO</b> FINE EDGE	31-001705	0-13658-13043-2	30-000641	0-13658-13253-5	Blade Length: 2.75" Overall Length: 6.25" Closed Length: 3.63" Weight: 2.0 oz Handle: G-10
	 	<b>SWAGGER™ AO</b> SERRATED EDGE	31-001709	0-13658-13046-3	30-000642	0-13658-13254-2	Blade Length: 3.25" Overall Length: 7.5" Closed Length: 4.25" Weight: 2.8 oz Handle: G-10
		<b>UPPERCUT™</b> FINE EDGE	31-001727	0-13658-13068-5	30-000650	0-13658-13261-0	Blade Length: 2.0" Overall Length: 4.0" Weight: .8 oz Sheath: Zytel 101

# KNIVES



## FIXED BLADE

		CLAM	CLAM UPC	BOX	BOX UPC	SPECIFICATIONS
						Blade Length: 4.25" Overall Length: 9.25" Weight: 4.9 oz Weight with sheath: 9.6 oz Handle: Fiberglass Reinforced Nylon Blade Steel: 154CM
				30-000598	0-13658-13003-6	
						Blade Length: 2.92" Overall Length: 8.12" Weight: 3.04 oz Handle: Nylon Overmold
		31-001856	0-13658-13174-3	30-000608	0-13658-13172-9	
						Blade Length: 4.0" Overall Length: 8.875" Weight: 3.9 oz Weight with sheath: 5.1 oz Handle: Fiberglass Reinforced Nylon Blade Steel: S30V
				30-000528	0-13658-12821-7	
						Blade Length: 3.41" Overall Length: 7.28" Weight: 3.0 oz Sheath: Molded Plastic Handle: TacHide™
		45803	0-13658-45803-1	05803	0-13658-05803-3	
						Blade Length: 3.38" Overall Length: 7.5" Weight: 3.3 oz Sheath: Molded Plastic Handle: TacHide™
		31-000559	0-13658-11795-2			
						Blade Length: 4.84" Overall Length: 10.59" Weight: 11.4 oz Sheath: Ballistic Nylon with Fire Retardant Coating
		22-41463	0-13658-41463-1	22-01626	0-13658-01626-2	
						Handle: TacHide™ Black Blade Steel: 420HC
		22-41629	0-13658-41629-1	22-01463	0-13658-01463-3	
						
		22-41629	0-13658-41629-1	22-01629	0-13658-01629-3	

# FIXED BLADE



## LMF™ II SURVIVAL

SERRATED EDGE 22-41400

COYOTE BROWN HANDLE, 2 LEG STRAPS, STRAP CUTTER, SHEATH

CLAM CLAM UPC BOX BOX UPC  
0-13658-41400-6 22-01400 0-13658-01400-8



### SPECIFICATIONS

Blade Length: 4.84"  
Overall Length: 10.59"  
Weight: 11.4 oz  
Sheath: Ballistic Nylon with Fire Retardant Coating  
Handle: TacHide™ Coyote Brown



## MARK II™

DOUBLE SERRATED EDGE

22-01874 0-13658-01874-7

Blade Length: 6.5"  
Overall Length: 11.75"  
Weight: 8.0 oz  
Sheath: Ballistic Nylon  
Handle: Aluminum  
Blade Steel: 420HC



PRODIGY™  
SERRATED EDGE  
DROP POINT 22-41121

0-13658-41121-0 22-01121 0-13658-01121-2

Blade Length: 4.75"  
Overall Length: 9.75"  
Weight: 7.2 oz  
Sheath: Ballistic Nylon  
Handle: TacHide™  
Blade Steel: 420HC



PRODIGY™  
SERRATED EDGE  
TANTO 31-000558

0-13658-11793-8

Blade Length: 9.75"  
Overall Length: 9.5"  
Weight: 7.2 oz  
Sheath: Lined Nylon Digital Camo  
Handle: TacHide™  
Blade Steel: 420HC



SILVER TRIDENT™  
DOUBLE SERRATED EDGE  
154CM

06995 0-13658-06995-4

Blade Length: 6.18"  
Overall Length: 11.22"  
Weight: 17.4 oz  
Sheath: Lined Ballistic Nylon  
Handle: Hytrel®  
Blade Steel: 154CM



STEADFAST™  
FINE EDGE 22-01120

0-13658-01120-5

Blade Length: 5.9"  
Overall Length: 10.6"  
Weight: 11.1 oz  
Sheath: Ballistic Nylon  
Handle: TacHide™



WARRANT™  
SERRATED EDGE  
TANTO 31-000560

0-13658-11797-6

Blade Length: 4.5"  
Overall Length: 9.5"  
Weight: 5.4 oz  
Sheath: Lined Nylon Digital Camo with Leg Straps  
Handle: Aluminum



# FOLDING CLIP



		CLAM	CLAM UPC	BOX	BOX UPC	SPECIFICATIONS	
		<b>06 AUTOMATIC™</b> SERRATED EDGE DROP POINT - S30V <i>Automatic knives available through authorized dealers only.</i>		30-000377	0-13658-12253-6	Blade Length: 3.8" Overall Length: 8.5" Closed Length: 4.7" Weight: 7.0 oz Handle: Aluminum Blade Steel: S30V	
		<b>06 AUTOMATIC™</b> SERRATED EDGE TANTO - S30V <i>Automatic knives available through authorized dealers only.</i>		22-01055	0-13658-01055-0	Blade Length: 3.8" Overall Length: 8.5" Closed Length: 4.7" Weight: 7.0 oz Handle: Aluminum Blade Steel: S30V	
		<b>06 AUTOMATIC™</b> SERRATED EDGE TANTO <i>Automatic knives available through authorized dealers only.</i>		30-000380	0-13658-12256-7	Blade Length: 3.8" Overall Length: 8.5" Closed Length: 4.7" Weight: 6.3 oz Handle: G-10 Blade Steel: S30V	
		<b>06 F.A.S.T.™</b> SERRATED EDGE TANTO	31-000216	0-13658-11375-6	30-000118	0-13658-11374-9	Blade Length: 3.8" Overall Length: 8.6" Closed Length: 4.8" Weight: 5.7 oz Handle: G-10
		<b>ANSWER™ F.A.S.T.</b> FINE EDGE	22-41970	0-13658-11148-6			Blade Length: 3.25" Overall Length: 7.85" Closed Length: 4.6" Weight: 4.9 oz Handle: Anodized Aluminum with textured inlay
		<b>ANSWER™ F.A.S.T. SM</b> FINE EDGE	31-000578	0-13658-11813-3			Blade Length: 2.75" Overall Length: 6.25" Closed Length: 3.75" Weight: 2.6 oz Handle: Anodized Aluminum with textured inlay
		<b>ANSWER™ F.A.S.T. XL</b> SERRATED EDGE TANTO	31-000581	0-13658-11819-5			Blade Length: 4.0" Overall Length: 9.25" Closed Length: 5.5" Weight: 7.0 oz Handle: Anodized Aluminum with textured inlay
		<b>APPLEGATE-FAIRBAIRN™ COVERT</b> SERRATED EDGE DOUBLE BEVEL	05785	0-13658-05785-2			Blade Length: 3.78" Overall Length: 8.7" Closed Length: 4.92" Weight: 4.2 oz Handle: Glass-filled Nylon Blade Steel: 154CM

# FOLDING CLIP



		CLAM	CLAM UPC	BOX	BOX UPC	SPECIFICATIONS
						<b>APPLEGATE-FAIRBAIRN™ COVERT</b> SERRATED EDGE DOUBLE BEVEL Blade Length: 3.78" Overall Length: 8.7" Closed Length: 4.92" Weight: 4.2 oz Handle: Glass-filled Nylon Blade Steel: 154CM
				30-000137	0-13658-11411-1	<b>APPLEGATE-FAIRBAIRN™ COVERT AUTOMATIC™</b> SERRATED EDGE S30V <i>Automatic knives available through authorized dealers only</i> Blade Length: 3.78" Overall Length: 8.7" Closed Length: 4.92" Weight: 5.0 oz Handle: 6061 Aluminum Blade Steel: S30V
		22-41966	0-13658-41966-7	22-01966	0-13658-01966-9	<b>APPLEGATE-FAIRBAIRN™ COVERT F.A.S.T.</b> SERRATED EDGE Blade Length: 3.7" Overall Length: 8.7" Closed Length: 5.0" Weight: 4.9 oz Handle: G-10
		46924	0-13658-46924-2			<b>APPLEGATE-FAIRBAIRN™ MINI COVERT</b> SERRATED EDGE Blade Length: 2.91" Overall Length: 6.65" Closed Length: 3.74" Weight: 2.2 oz Handle: Glass-filled Nylon
		22-47177	0-13658-47177-1			<b>APPLEGATE-FAIRBAIRN™ MINI COVERT</b> SERRATED EDGE Blade Length: 2.91" Overall Length: 6.65" Closed Length: 3.74" Weight: 2.2 oz Handle: Glass-filled Nylon
				30-000244	0-13658-11811-9	<b>APPLEGATE-FAIRBAIRN™ MINI COVERT AUTOMATIC</b> SERRATED EDGE S30V <i>Automatic knives available through authorized dealers only</i> Blade Length: 2.8" Overall Length: 6.5" Closed Length: 3.75" Weight: 2.1 oz Handle: Aluminum Blade Steel: S30V
		22-41967	0-13658-41967-4	22-01967	0-13658-01967-6	<b>APPLEGATE-FAIRBAIRN™ MINI COVERT F.A.S.T.</b> SERRATED EDGE Blade Length: 2.9" Overall Length: 6.85" Closed Length: 3.95" Weight: 3.2 oz Handle: G-10
				30-000378	0-13658-12254-3	<b>D.M.F.™ AUTOMATIC</b> SERRATED EDGE MODIFIED CLIP POINT - S30V <i>Automatic knives available through authorized dealers only.</i> Blade Length: 3.5" Overall Length: 7.35" Closed Length: 3.85" Weight: 8.5 oz Handle: G-10 Blade Steel: S30V
				30-000379	0-13658-12255-0	<b>D.M.F.™ AUTOMATIC</b> SERRATED EDGE TANTO S30V <i>Automatic knives available through authorized dealers only.</i> Blade Length: 3.5" Overall Length: 7.35" Closed Length: 3.85" Weight: 8.5 oz Handle: G-10 Blade Steel: S30V

# FOLDING CLIP






		CLAM	CLAM UPC	BOX	BOX UPC	SPECIFICATIONS
	<b>D.M.F.™ MANUAL</b> SERRATED EDGE MODIFIED CLIP POINT	31-000582	0-13658-11821-8			Blade Length: 3.50" Overall Length: 8.38" Closed Length: 4.75" Weight: 6.2 oz Handle: G-10
	<b>D.M.F.™ MANUAL</b> SERRATED EDGE TANTO	31-000583	0-13658-11823-2			Blade Length: 3.50" Overall Length: 8.38" Closed Length: 4.75" Weight: 6.2 oz Handle: G-10
	<b>EMERSON ALLIANCE AUTOMATIC™</b> SERRATED EDGE 154CM <i>Automatic knives available through authorized dealers only.</i>			22-07158	0-13658-07158-2	Blade Length: 3.44" Overall Length: 8.7" Closed Length: 5.26" Weight: 6.0 oz Handle: Anodized Aluminum Blade Steel: 154CM
	<b>EVO™ JR. - TI-COATED</b> SERRATED EDGE FINE EDGE	22-41493 22-41492	0-13658-41493-8 0-13658-41492-1			Blade Length: 2.75" Overall Length: 6.35" Closed Length: 3.6" Weight: 1.8 oz Handle: Anodized Aluminum
	<b>EVO™ MID - TI-COATED</b> SERRATED EDGE TANTO	31-000486	0-13658-11689-4			Blade Length: 3.12" Overall Length: 7.12" Closed Length: 4.0" Weight: 2.4 oz Handle: Anodized Aluminum
	<b>EVO™ - TI-COATED</b> SERRATED EDGE FINE EDGE	22-41432 22-41433	0-13658-41432-7 0-13658-41433-4			Blade Length: 3.43" Overall Length: 7.95" Closed Length: 4.52" Weight: 2.8 oz Handle: Anodized Aluminum
	<b>HINDERER CLS™</b> SERRATED EDGE	22-41870	0-13658-41870-7	22-01870	0-13658-01870-9	Blade Length: 3.5" Overall Length: 8.5" Closed Length: 5.0" Weight: 5.6 oz Handle: Glass-filled Nylon
	<b>ICON™ TANTO</b> SERRATED EDGE TANTO	31-000372	0-13658-11568-2			Blade Length: 4.25" Overall Length: 9.55" Closed Length: 5.3" Weight: 4.68 oz Handle: Anodized with textured inlay
	<b>KIOWA™</b> SERRATED EDGE TANTO	22-41405	0-13658-41405-1			Blade Length: 2.99" Overall Length: 7.4" Closed Length: 4.41" Weight: 3.4 oz Handle: Glass-filled Nylon

## FOLDING CLIP



	CLAM	CLAM UPC	BOX	BOX UPC	SPECIFICATIONS	
	<b>REMIX™ TACTICAL</b> SERRATED EDGE TANTO	31-001098	0-13658-12483-7	30-000433	0-13658-12484-4	Blade Length: 3.0" Overall Length: 7.86" Closed Length: 4.86" Weight: 4.6 oz Handle: G-10 Composite
	<b>MINI SWAGGER™</b> FINE EDGE	31-000593	0-13658-11837-9			Blade Length: 2.75" Overall Length: 6.25" Closed Length: 3.5" Weight: 2.9 oz Handle: G-10
	<b>SWAGGER™</b> SERRATED EDGE	31-000594	0-13658-11839-3			Blade Length: 3.31" Overall Length: 7.5" Closed Length: 4.25" Weight: 4.4 oz Handle: G-10
	<b>TORCH™ I</b> SERRATED EDGE TANTO	22-41584	0-13658-41584-3			Blade Length: 3.25" Overall Length: 6.25" Closed Length: 3.5" Weight: 3.3 oz Handle: Glass-filled Nylon
	<b>TORCH™ II</b> SERRATED EDGE TANTO	22-41586	0-13658-41586-9			Blade Length: 3.5" Overall Length: 8.25" Closed Length: 4.75" Weight: 5.7 oz Handle: G-10

## FOLDING SHEATH

	<b>APPLEGATE-FAIRBAIRN™ COMBAT FOLDER WITH SHEATH</b> SERRATED EDGE	45780	0-13658-45780-5			Blade Length: 4.48" Overall Length: 10.06" Closed Length: 5.58" Weight: 7.4 oz Sheath: Ballistic Nylon Handle: Glass-filled Nylon Black
	<b>HINDERER CLS™</b> SERRATED EDGE	22-41870	0-13658-41870-7	22-01870	0-13658-01870-9	Blade Length: 3.5" Overall Length: 8.5" Closed Length: 5.0" Weight: 5.6 oz Handle: Glass-filled Nylon
	<b>HINDERER RESCUE™</b> SERRATED EDGE BLUNT TIP	22-41534	0-13658-41534-8	22-01534	0-13658-01534-0	Blade Length: 3.5" Overall Length: 8.5" Closed Length: 5.1" Weight: 5.6 oz Sheath: Ballistic Nylon Handle: Glass-filled Nylon

# MULTI-TOOLS



## MINI/KEYCHAIN TOOLS



10 TOOL MULTI-PLIERS

**DIME™**  
**BLACK**

CLAM	CLAM UPC	BOX	BOX UPC
31-001134	0-13658-12555-1	30-000469	0-13658-12556-8

### SPECIFICATIONS

Overall Length: 4.25"  
Closed Length: 2.75"  
Weight: 2.2 oz

Stainless Steel  
Fine Edge Blade  
Spring Loaded Jaw  
Spring Loaded Needlenose Pliers  
Spring Loaded Scissors  
Retail Package Opener  
Wire Cutters  
File  
Medium Flat Driver  
Bottle Opener  
Tweezers

## POCKET/CLIP TOOLS



9 TOOL MULTI-PLIERS

**CRUCIAL™**  
**BLACK**

CLAM	CLAM UPC	BOX	BOX UPC
31-001518	0-13658-12987-0	30-000587	0-13658-12988-7

Overall Length: 5.5"  
Closed Length: 3.6"  
Weight: 5.0 oz

Liner Lock  
Stainless Steel  
Needle Nose Pliers  
1/2 Fine Edge & Serrated Blade  
Phillips Driver  
Large Flat Driver  
Bottle Opener  
V Cut Wire Cutters  
Strap Cutter  
Pocket Clip  
Regular Pliers

## FULL SIZE TOOLS



14 TOOL MULTI-PLIERS

**DIESEL™**  
**BLACK**

CLAM	CLAM UPC
22-41545	0-13658-41545-4



Overall Length: 6.61"  
Closed Length: 4.92"  
Weight: 8.6 oz

Saf.T.Plus™  
Stainless Steel  
Needle Nose Pliers  
1/2 Fine Edge & Serrated Blade  
Saw  
Phillips Driver  
Small, Medium & Large Flat Driver  
Bottle Opener & Can Opener  
File  
Scissors  
Wire Cutters  
Lanyard Ring  
Black Ballistic Nylon Sheath

# FULL SIZE TOOLS



## eFECT™

CLAM	CLAM UPC	BOX	BOX UPC
31-000049	0-13658-11188-2		

### SPECIFICATIONS

Overall Length: 8.0"  
 Closed Length: 3.5"  
 Weight: 3.8 oz

Saf.T.Plus™  
 Stainless Steel - Black  
 Interchangeable Tool Component:  
 OTIS™ Nylon End Brush  
 Front Sight Post Adjuster  
 Flat Driver/Scraper  
 Interchangeable Tool Component:  
 OTIS™ Curved Pick  
 Punch  
 Scraper  
 Black Ballistic Nylon Sheath



## FLIK™ BLACK

CLAM	CLAM UPC	BOX	BOX UPC
22-41638	0-13658-41638-3	22-01638	0-13658-01638-5

Overall Length: 5.8"  
 Closed Length: 4.4"  
 Weight: 8.75 oz

Saf.T.Plus™  
 Stainless Steel  
 Needle Nose Pliers  
 1/2 Fine Edge & Serrated Blade  
 Saw  
 Phillips Driver  
 Small & Medium Flat Driver  
 Bottle Opener & Can Opener  
 Scissors  
 V Cut Wire Cutters  
 Lanyard Ring  
 Black Ballistic Nylon Sheath



## MP 400 COMPACT SPORT BLACK

CLAM	CLAM UPC	BOX	BOX UPC
22-45509	0-13658-45509-2	22-05509	0-13658-05509-4

Overall Length: 5.63"  
 Closed Length: 4.37"  
 Weight: 6.8 oz










Saf.T.Plus™  
 Stainless Steel  
 Needle Nose Pliers  
 1/2 Fine Edge & Serrated Blade  
 Phillips Driver  
 Small, Medium & Large Flat Driver  
 Bottle Opener & Can Opener  
 Scissors  
 Wire Cutters & Wire Stripper  
 Pocket Clip  
 Regular Pliers  
 Black Ballistic Nylon Sheath





# FULL SIZE TOOLS



	CLAM	CLAM UPC	BOX	BOX UPC	SPECIFICATIONS	
   <div style="position: absolute; top: 170px; left: 215px; background-color: black; color: white; padding: 2px;">14 TOOL MULTI-PLIERS</div>	<b>MP 600 D.E.T.<sup>™</sup></b> <b>BLACK</b>		30-000471	0-13658-12561-2	<p>Overall Length: 6.61"            Closed Length: 5.04"            Weight: 9.0 oz</p> <p>Saf.T.Plus<sup>™</sup>            Stainless Steel - Black            Needle Nose Pliers With            Blasting Cap Crimper            Wire Cutter &amp; Wire Crimper            C4 Punch            Fine Edge Knife            Phillips Driver            Large Flat Driver            Remgrit<sup>™</sup> Saw With            Universal Coupler            Can Opener            File            Lanyard Ring            Black Ballistic Nylon Sheath</p>	
   <div style="position: absolute; top: 440px; left: 215px; background-color: black; color: white; padding: 2px;">14 TOOL MULTI-PLIERS</div>	<b>MP 600-ST<sup>™</sup></b> <b>BLACK</b>	31-001519	0-13658-12989-4	30-000588	0-13658-12990-0	<p>Overall Length: 6.61"            Closed Length: 5.04"            Weight: 8.2 oz</p> <p>Saf.T.Plus<sup>™</sup>            Stainless Steel - Black            Needle Nose Pliers With            Blasting Cap Crimper            M4/M16 Front Sight Post            Adjustment Tool            Carbon Scraper            Fine &amp; Serrated Edge Knife            Carbide Wire Cutters            Long Reach Phillips Driver            Lanyard Ring            Can &amp; Bottle Openers            Black Ballistic Nylon Sheath</p>
   <div style="position: absolute; top: 700px; left: 215px; background-color: black; color: white; padding: 2px;">14 TOOL MULTI-PLIERS</div>	<b>MP 600 BASIC</b> <b>BLACK</b>	47550	0-13658-47550-2	07550	0-13658-07550-4	<p>Overall Length: 6.61"            Closed Length: 5.04"            Weight: 9.0 oz</p> <p>Saf.T.Plus<sup>™</sup>            Stainless Steel            Needle Nose Pliers            Fine Edge Knife            Serrated Edge Knife            Phillips Driver            Small, Medium &amp; Large Flat Driver            Ruler            Bottle Opener &amp; Can Opener            File            Wire Cutters            Wire Crimper            Lanyard Ring            Black Ballistic Nylon Sheath</p>

# FULL SIZE TOOLS



CLAM

CLAM UPC

BOX

BOX UPC

SPECIFICATIONS



14 TOOL MULTI-PLIERS

## MP 600 BASIC - BLUNTNOSE - TUNGSTEN CARBIDE BLACK

07520

0-13658-07520-7



Overall Length: 6.38"  
Closed Length: 4.88"  
Weight: 9.0 oz

- Saf.T.Plus™
- Stainless Steel
- BluntNose Pliers
- Fine Edge Knife
- Serrated Edge Knife
- Phillips Driver
- Small, Medium & Large Flat Driver
- Ruler
- Bottle Opener & Can Opener
- File
- Tungsten Carbide Wire Cutters
- Wire Crimper
- Lanyard Ring
- Berry Compliant Ballistic Nylon Sheath





# GEAR

## LIGHTS



CLAM CLAM UPC BOX BOX UPC

SPECIFICATIONS



### INFINITY ULTRA TASK LIGHT™

**BLACK** 22-80012 0-13658-80012-0

○ WHITE LIGHT

Overall Length: 3.31"  
Weight: 2.2 oz  
Lumens: 8  
Runtime: 32 hrs  
Batteries: [1] AA



### RECON™ TASK LIGHT

22-80016 0-13658-80016-8

○ WHITE LIGHT ● RED LIGHT ● NVIS LIGHT ● BLUE LIGHT

Overall Length: 3.31"  
Weight: 2.6 oz  
Lumens: 3  
Runtime: 28 hrs  
Batteries: [1] AA

## SHARPENER



### DOWNRANGE SHARPENER™

31-001855 0-13658-13173-6 30-000600 0-13658-13015-9

Overall Length: 4.35"  
Thickness: .5"  
Width: 1.44"  
Weight: 2.2 oz

Coated in TAN499 Ceramic  
Replaceable Carbide Cutters  
Large/Small Diamond Coated  
Rod for Serrations  
Flat Diamond Coated Plate  
for Finishing  
550 Lanyard  
Made in the USA

## SPADE



### E-TOOL™ WITH SERRATED BLADE AND PICK

22-01945 0-13658-01945-4

Overall Length: 23.39"  
Closed Length: 9.37"  
Weight: 37.3 oz

Serrated Edge  
Cast Pick Attachment  
Glass-Filled Nylon Handle  
Powder Coated Boron Carbon Steel  
Spade  
Anodized Aluminium Shaft  
Forged Steel Head  
Molded Plastic Sheath

# NEW FOR 2013



NEW FOR 2013



## D-1 - 3" ASSISTED OPENING KNIFE

CLAM 31-001403 CLAM UPC 0-13658-12910-8 BOX BOX UPC

SPECIFICATIONS  
Blade Length: 3.0"  
Overall Length: 7.0"  
Closed Length: 4.28"  
Weight: 3.3 oz  
Handle: G-10

NEW FOR 2013



## J-1 - 3" ASSISTED OPENING KNIFE

CLAM 31-001404 CLAM UPC 0-13658-12911-5 BOX BOX UPC

SPECIFICATIONS  
Blade Length: 3.0"  
Overall Length: 6.6"  
Closed Length: 4.0"  
Weight: 2.46 oz  
Handle: G10

NEW FOR 2013



## K-3 - 3" ASSISTED OPENING KNIFE

CLAM 31-001402 CLAM UPC 0-13658-12909-2 BOX BOX UPC

SPECIFICATIONS  
Blade Length: 3.0"  
Overall Length: 7.13"  
Closed Length: 4.19"  
Weight: 3.77 oz  
Handle: G10

NEW FOR 2013



## D-2 - 2.5" CLIP KNIFE

CLAM 31-001389 CLAM UPC 0-13658-12900-9 BOX BOX UPC

SPECIFICATIONS  
Blade Length: 2.5"  
Overall Length: 5.94"  
Closed Length: 3.5"  
Weight: 2.07 oz  
Handle: Polymer

NEW FOR 2013



## D-2 - 3" CLIP

CLAM 31-001388 CLAM UPC 0-13658-12899-6 BOX BOX UPC

SPECIFICATIONS  
Blade Length: 3.0"  
Overall Length: 7.12"  
Closed Length: 4.19"  
Weight: 2.87 oz  
Handle: Polymer

NEW FOR 2013



## K-3 - 2.5" CLIP KNIFE

CLAM 31-001368 CLAM UPC 0-13658-12895-8 BOX BOX UPC

SPECIFICATIONS  
Blade Length: 2.5"  
Overall Length: 5.88"  
Closed Length: 3.43"  
Weight: 1.79 oz  
Handle: Polymer

NEW FOR 2013



## K-3 - 3" CLIP KNIFE

CLAM 31-001235 CLAM UPC 0-13658-12894-1 BOX BOX UPC

SPECIFICATIONS  
Blade Length: 3.0"  
Overall Length: 7.13"  
Closed Length: 4.13"  
Weight: 2.71 oz  
Handle: Polymer

# NEW FOR 2013



NEW FOR 2013



## D-2 - 2.5" FIXED BLADE KNIFE

CLAM 31-001383 CLAM UPC 0-13658-12902-3 BOX BOX UPC

SPECIFICATIONS  
Blade Length: 2.5"  
Overall Length: 5.94"  
Closed Length: n/a  
Weight: 1.79 oz  
Handle: Polymer

NEW FOR 2013



## D-2 - 3" FIXED BLADE KNIFE

CLAM 31-001241 CLAM UPC 0-13658-12901-6 BOX BOX UPC

SPECIFICATIONS  
Blade Length: 3.0"  
Overall Length: 7.13"  
Closed Length: n/a  
Weight: 2.99 oz  
Handle: Polymer

NEW FOR 2013



## K-3 - 2.5" FIXED BLADE KNIFE

CLAM 31-001368 CLAM UPC 0-13658-12895-8 BOX BOX UPC

SPECIFICATIONS  
Blade Length: 2.5"  
Overall Length: 6"  
Closed Length: n/a  
Weight: 2.01 oz  
Handle: Polymer

NEW FOR 2013



## K-3 - 3" FIXED BLADE KNIFE

CLAM 31-001372 CLAM UPC 0-13658-12896-5 BOX BOX UPC

SPECIFICATIONS  
Blade Length: 3.0"  
Overall Length: 7.19"  
Closed Length: n/a  
Weight: 3.42 oz  
Handle: Polymer

NEW FOR 2013



8 TOOL MULTI-PLIERS

## D-2 MINI-TOOL

CLAM 31-001371 CLAM UPC 0-13658-12903-0 BOX BOX UPC

SPECIFICATIONS  
Overall Length: 4.19"  
Closed Length: 2.75"  
Weight: 2.99 oz

Needlenose Pliers  
Blade Length: 1.5 inches  
Blade Steel Type: Stainless Steel  
Handle Material: Polymer  
Locking Mechanism: Friction Lock

NEW FOR 2013



8 TOOL MULTI-PLIERS

## K-3 MINI-TOOL

CLAM 31-001391 CLAM UPC 0-13658-12898-9 BOX BOX UPC

SPECIFICATIONS  
Overall Length: 4.19"  
Closed Length: 2.75"  
Weight: 2.99 oz

Needlenose Pliers  
Blade Length: 1.5 inches  
Blade Steel Type: Stainless Steel  
Handle Material: Polymer  
Locking Mechanism: Friction Lock





## FOR WELL-MADE TOOLS BUILT FOR DAILY ABUSE

on the job site, Gerber's Industrial line can't be matched. Constructed with the most advanced materials, that are both lightweight and indestructible, every tool is designed for all-day efficiency and durability. What you'll need to finish the job is already in your hand.

INDUSTRIAL

# NEW FOR 2013



CLAM CLAM UPC BOX BOX UPC

SPECIFICATIONS

31-001142 0-13658-12642-8 30-000477 0-13658-12643-5

Overall Length: 6.75" - 5.9"  
 Closed Length: 4.2"  
 Weight: 8 oz


- Forged Jaws
- G10 Handles
- Bottle Opener/Pry Bar
- Butterfly Opening Spring Loaded Jaws
- Large Fine Edge Blade
- Wire Stripper
- Diagonal Cutters
- Magnetic Bit Driver w/ #2 Philips Driver
- Large Fully Serrated Blade
- Large Flat Driver
- Small Flat Driver
- Utility Blade/Scraper



12 TOOL MULTI-PLIERS

SHIFT™

NEW FOR 2013



# KNIVES

## UTILITY FIXED BLADE



CLAM CLAM UPC BOX BOX UPC

### SPECIFICATIONS



#### SAFETY STRAP & BOX CUTTER™

FINE EDGE 31-000665 0-13658-11921-5

Overall Length: 6.0"  
Weight: 2.08 oz  
Handle: Glass-filled Nylon

Includes 5-pack blades  
Reversible/removable blade guard



#### TRANSIT 2-IN-1™

31-001039 0-13658-12404-2 30-000416 0-13658-12504-9

Overall Length: 5.75"  
Closed Length: 5.5"  
Weight: 2.6 oz

## UTILITY FOLDING CLIP



#### E.A.B LITE™

FINE EDGE 31-000345 0-13658-11527-9

Blade Length: 1.5"  
Overall Length: 5.1"  
Closed Length: 2.85"  
Weight: 2.4 oz  
Handle: Stainless Steel



#### E.A.B POCKET KNIFE™

FINE EDGE 22-41830 0-13658-41830-1

Blade Length: 1.5"  
Overall Length: 5.1"  
Closed Length: 2.85"  
Weight: 2.2 oz  
Handle: Stainless Steel



#### EDGE ALUMINUM™

FINE EDGE  
BLACK 31-000666 0-13658-11922-2  
BLUE 31-000667 0-13658-11923-9

Blade Length: 1.12"  
Overall Length: 6.5"  
Closed Length: 3.87"  
Weight: 3.52 oz  
Handle: Anodized Aluminum



#### EDGE TACHIDE™

FINE EDGE  
BLACK 31-000669 0-13658-11925-3  
BLUE 31-000668 0-13658-11924-6

Blade Length: 1.12"  
Overall Length: 6.12"  
Closed Length: 3.75"  
Weight: 2.8 oz  
Handle: TacHide™

## UTILITY FOLDING CLIP



**TRANSIT™**  
FINE EDGE

CLAM	CLAM UPC	BOX	BOX UPC
31-001085	0-13658-12458-5	30-000425	0-13658-12458-5

### SPECIFICATIONS

Blade Length:	1.3"
Overall Length:	5.15"
Closed Length:	4.14"
Weight:	2.63 oz
Handle:	Textured Rubber

Includes 5-pack blades  
Pocket clip

## FOLDING CLIP



**OBSIDIAN™**  
SERRATED EDGE  
FINE EDGE

22-41022	0-13658-41022-0		
22-41021	0-13658-41021-3	22-01021	0-13658-01021-5

Blade Length:	3.13"
Overall Length:	7.06"
Closed Length:	3.93"
Weight:	4.6 oz
Handle:	Glass-filled Nylon



**RIDGE™**  
SERRATED EDGE  
TANTO

45898	0-13658-45898-7
-------	-----------------












Blade Length:	1.98"
Overall Length:	4.87"
Closed Length:	2.89"
Weight:	1.4 oz
Handle:	Stainless Steel





# MULTI-TOOLS



	CLAM	CLAM UPC	BOX	BOX UPC	SPECIFICATIONS	
  	<b>CABLE DAWG™</b>		30-000399	0-13658-12355-7	Overall Length: 7.5" Weight: 13.8 oz  Wire/Cable Cutter CAT5 Jacket Cutter Spring Loaded Jaw, RJ45 Crimper Head Wire Strippers Combo Edge Knife Blade with Jacket Cutter Detachable Component Handle Magnetic Driver Extension Multiple Driver Storage Compartment Ballistic Nylon Sheath	
    	<b>DIESEL™</b>	22-41470	0-13658-41470-9	22-01470	0-13658-01470-1	Overall Length: 6.61" Closed Length: 4.92" Weight: 8.6 oz  Saf.T.Plus™ Stainless Steel Ballistic Nylon Sheath Needle Nose Pliers 1/2 Fine Edge & Serrated Blade Saw Phillips Driver Small, Medium & Large Flat Driver Bottle Opener & Can Opener Wire Cutters Lanyard Ring Scissors File
   	<b>Flik™</b>	22-41054	0-13658-41054-1	22-01054	0-13658-01054-3	Overall Length: 5.8" Closed Length: 4.4" Weight: 8.75 oz  Saf.T.Plus™ Stainless Steel Ballistic Nylon Sheath Needle Nose Pliers 1/2 Fine Edge & Serrated Blade Saw Phillips Driver Small & Medium Flat Driver Lanyard Ring Bottle Opener & Can Opener Scissors V Cut Wire Cutters

CLAM CLAM UPC BOX BOX UPC

SPECIFICATIONS

**GROUNDBREAKER™**

31-001440 0-13658-12790-6 30-000454 0-13658-12470-7

Overall Length: 9"  
Width: 2.75"



Industrial Grade Wire Cutters  
Industrial Grade Wire Strippers  
Locking Utility Knife  
Locking Drywall Saw Blade & Driver  
with 6 Interchangeable bits  
Heavy-Duty Belt Sheath  
5 Extra Replacement Blades



14 TOOL MULTI-PLIERS

**MP 600 BASIC**

47530 0-13658-47530-4 07530 0-13658-07530-6

Overall Length: 6.61"  
Closed Length: 5.04"  
Weight: 9.0 oz



Saf.T.Plus™  
Stainless Steel  
Ballistic Nylon Sheath  
Needle Nose Pliers  
Fine Edge Knife  
Serrated Knife  
Phillips Driver  
Small, Medium & Large Flat Driver  
Wire Cutters & Wire Crimper  
Bottle Opener & Can Opener  
File  
Ruler  
Lanyard Ring



14 TOOL MULTI-PLIERS

**MP 600 - TUNGSTEN CARBIDE BLUNTNOSE**

07500 0-13658-07500-9

Overall Length: 6.38"  
Closed Length: 4.88"  
Weight: 9.0 oz



Saf.T.Plus™  
Stainless Steel  
Ballistic Nylon Sheath  
Blunt Nose Pliers  
Fine Edge Knife  
Serrated Knife  
Phillips Driver  
Small, Medium & Large Flat Driver  
Tungsten Carbide Wire Cutters  
Wire Crimper  
Bottle Opener & Can Opener  
File  
Ruler  
Lanyard Ring

CLAM CLAM UPC BOX BOX UPC

SPECIFICATIONS



14 TOOL MULTI-PLIERS

**MP 600 PRO SCOUT**

47563 0-13658-47563-2 07563 0-13658-07563-4

Overall Length: 6.61"  
Closed Length: 5.04"  
Weight: 9.0 oz



Saf.T.Plus™  
Stainless Steel  
Ballistic Nylon Sheath  
Needle Nose Pliers  
1/2 Fine & Serrated Edge Blade  
Remgrit® Saw  
Phillips Driver  
Small & Medium Flat Driver  
Ruler  
Wire Cutters & Wire Crimper  
Bottle Opener & Can Opener  
Scissors  
File



14 TOOL MULTI-PLIERS

**MP 600 PRO SCOUT WITH TOOL KIT**

07564 0-13658-07564-1

Overall Length: 6.61"  
Closed Length: 5.04"  
Weight: 9.0 oz



Saf.T.Plus™  
Stainless Steel  
Ballistic Nylon Sheath  
Needle Nose Pliers  
1/2 Fine & Serrated Edge Blade  
Remgrit® Saw  
Phillips Driver  
Small & Medium Flat Driver  
Ruler  
Wire Cutters & Wire Crimper  
Bottle Opener & Can Opener  
Scissors  
File  
Tool Kit



12 TOOL MULTI-PLIERS

**MP 800 LEGEND™**

48239 0-13658-48239-5 08239 0-13658-08239-7

Overall Length: 6.57"  
Closed Length: 4.29"  
Weight: 9.8 oz



Saf.T.Plus™  
Stainless Steel - E-Coat  
Ballistic Nylon Sheath  
Needle Nose Pliers  
1/2 Fine Edge & Serrated Blade  
Remgrit® Saw  
Phillips Driver  
Small, Medium & Large Flat Driver  
Bottle Opener  
Scissors  
File  
Tungsten Carbide Cutters

# ACCESSORIES



CLAM

CLAM UPC

BOX

BOX UPC

SPECIFICATIONS



## TUNGSTEN CARBIDE CUTTER INSERT REPLACEMENTS

48252

0-13658-48252-4

Replacements Fit the Following Multi-Pliers: MP 600 Basic (select models only), MP 800 Legend™



## TOOL KIT

22-49445

0-13658-49445-9

Contains an Adapter, Three Different Sizes of Flathead Bits, Cross Point Bits and Hex Head Bits. Fits Flik™, Diesel™, Grappler™




## TOOL KIT

45200

0-13658-45200-8

Contains an Adapter, Three Different Sizes of Flathead Bits, Cross Point Bits and Hex Head Bits. Fits MP 400, MP 600, MP 800



# DISPLAYS



## SINGLE MULTI-TOOL DISPLAY

**P/N:** 30-000572 **UPC:** 0-13658-12865-1  
**Dimensions:** 2.75" W x 3.7" D x 2.5" H




## SINGLE KNIFE DISPLAY

**P/N:** 30-000569 **UPC:** 0-13658-12862-0  
**Dimensions:** 4.125" W x 1.81" D x 1.93" H



## DOUBLE KNIFE DISPLAY

**P/N:** 30-000570 **UPC:** 0-13658-12863-7  
**Dimensions:** 4.375" W x 3.375" D x 2.375" H



## TRIPLE KNIFE DISPLAY

**P/N:** 30-000571 **UPC:** 0-13658-12864-4  
**Dimensions:** 4.625" W x 5.0" D x 2.82" H

# MERCHANDISE



## COFFEE MUG

P/N

UPC

30-000533

0-13658-12826-2



## TRAVEL COFFEE MUG

30-000534

0-13658-12827-4



## WATER BOTTLE

30-000535

0-13658-12828-6



*back*

## BASEBALL CAP

30-000536

0-13658-12829-7

# MERCHANDISE



## BEANIE HAT

P/N	UPC
30-000538	0-13658-12831-0



## MOUSE PAD

30-000543	0-13658-12836-1
-----------	-----------------



## TEE SHIRTS

MEDIUM	30-000539	0-13658-12832-3
LARGE	30-000540	0-13658-12833-0
X-LARGE	30-000541	0-13658-12834-7
XX-LARGE	30-000542	0-13658-12835-4



GERBER GEAR  
14200 SW 72ND AVENUE  
PORTLAND, OREGON 97224  
[GERBERGEAR.COM](http://GERBERGEAR.COM)

**FISKARS®**