

At Voltec, we know and understand that growth is directly related to new products. We strive to provide new and innovative products that positively impacts your ability to expand your market share and enhance your margins. As we continue to provide knowledgeable, prompt, efficient and friendly customer service, our goal is to surpass your expectations. Voltec Industries is where quality and value come together!

Innovative Products

Industry Leader in Custom Products



Breadth of Line



Compare the Quality



Table of Contents

<i>E-ZEELOCK® Locking Connector</i>	4-6
<i>Outdoor 300V Extension Cords</i>	7-8
<i>All Weather 300V Extension Cords</i>	9-10
<i>Outdoor 600V Extension Cords</i>	11
<i>Kwik Kustom Extension Cords/Quote Form</i>	12-14
<i>Adapters</i>	15-16
<i>Generator Adapters</i>	17
<i>Portable GFCIs</i>	18
<i>Temporary Power</i>	19
<i>Temporary Lighting</i>	20
<i>Wiring Devices</i>	21
<i>Workbench/Household Extension Cords</i>	22
<i>Replacement Cords for Power Tools</i>	23
<i>Range & Dryer Cords</i>	24
<i>A/C & Garbage Disposal Power Supply Cords</i>	25
<i>Open Cord Retractable Reels</i>	26
<i>Clamp Lighting</i>	27
<i>Incandescent Worklights</i>	28
<i>Incandescent Trouble Lights w/Retractable Reels</i>	29
<i>Economy Fluorescent Worklights</i>	30
<i>E-ZEELAMP Replacement</i>	31
<i>Professional Fluorescent Worklights</i>	32
<i>Fluorescent Retractable Reels</i>	33
<i>Halogen Worklights</i>	34-35
<i>Dusk to Dawn Metal Halide</i>	36
<i>LED Worklights</i>	37
<i>Lighting Replacement Parts</i>	37
<i>Booster Cables</i>	38
<i>Booster Power Packs</i>	39
<i>Battery Chargers/Testers</i>	40
<i>Power Inverters</i>	41
<i>RV/Marine</i>	42-45
<i>Convention Center Cords</i>	46
<i>Lighting Replacement Parts</i>	47
<i>NEMA Chart</i>	48
<i>Glossary</i>	49-53
<i>Competitors Cross Reference</i>	54-55
<i>Index of Parts</i>	56-60

Voltec Power & Lighting Regional Distribution Warehouses

- Chino, California
- Orlando, Florida
- Chicago, Illinois
- Kansas City, Missouri
- Newark, New Jersey
- Charlotte, No. Carolina
- Pittsburgh, Pennsylvania
- Seattle, Washington

AFFILIATES



The information contained in this catalog is presented solely as a guide to product selection and is reliable to the best of our knowledge. Any printing errors are subject to correction in future releases or reprints of this catalog. Voltec Industries has taken precautions, at the time of publication, to ensure the accuracy of the data and specifications presented herein, but reserves the right to modify, append or change the specifications of any and all products contained within this catalog at any time and without prior notice.

*Exclusively from
Voltec Power &
Lighting*



Locking Your Cord is E-ZEE as 1 ▪ 2 ▪ 3

1



Plug E-ZEE LOCK® Connector into male plug




Extension Cord is Locked

2



Close E-ZEE LOCK® latching mechanism onto the cable of the male plug. (Must attach to the cable, not the male plug)

3



Twist E-ZEE LOCK® to a Locking Fit

- UL & CSA Listed
- Securely connects power cords to stop annoying, unwanted disconnects
- Adds additional locking strength with a nylon arm, which is virtually unbreakable
- Extension cords are available with power indicator light
- Adapters are available with EZEELock®

**COMPARE
THE
QUALITY**



PRO SERIES product

Outdoor 300V SJTW Extension Cords -40°F TO 140°F

E-ZEE LOCK 3-Conductor 300V SJEOW Extension Cords with E-ZEELOCK™ and Lighted End cUL^{us}

ITEM PN#	CORD LENGTH	WIRE GAUGE	WIRE TYPE	WIRE COLOR	OUTLETS	PLUG TYPE	RECEPTACLE TYPE	POWER RATING AMPS	WATTS	PACK QTY
05-00111	25ft	14/3	SJTW	Org/Blck	1	5-15P	5-15R	15	1875	6
05-00112	50ft	14/3	SJTW	Org/Blck	1	5-15P	5-15R	15	1875	6
05-00113	100ft	14/3	SJTW	Org/Blck	1	5-15P	5-15R	13	1625	3
05-00105	25ft	12/3	SJTW	Yell/Blue/Blue	1	5-15P	5-15R	15	1875	12
05-00106	50ft	12/3	SJTW	Yell/Blue/Blue	1	5-15P	5-15R	15	1875	4
05-00107	100ft	12/3	SJTW	Yell/Blue/Blue	1	5-15P	5-15R	15	1875	2



All Weather Outdoor 300V SJEOW Extension Cords -58°F to 228°

ALL-FLEX
THE ALL WEATHER EXTENSION CORD

ALL-FLEX 3-Conductor 300V SJEOW Extension Cords with E-ZEELOCK™ and Lighted End cUL^{us}

ITEM PN#	CORD LENGTH	WIRE GAUGE	WIRE TYPE	WIRE COLOR	OUTLETS	PLUG TYPE	RECEPTACLE TYPE	POWER RATING AMPS	WATTS	PACK QTY
05-00138	25ft	14/3	SJEOW	Blue	1	5-15P	5-15R	15	1875	6
05-00139	50ft	14/3	SJEOW	Blue	1	5-15P	5-15R	15	1875	6
05-00140	100ft	14/3	SJEOW	Blue	1	5-15P	5-15R	13	1625	3
05-00141	25ft	12/3	SJEOW	Blue	1	5-15P	5-15R	15	1875	12
05-00142	50ft	12/3	SJEOW	Blue	1	5-15P	5-15R	15	1875	4
05-00143	100ft	12/3	SJEOW	Blue	1	5-15P	5-15R	15	1875	2





PRO SERIES product



Tested for Strength You can Count On!



Durable
Nylon
Locking Arm



Preventing
Unwanted
Disconnects


Adapters



Locking Plug to U-Ground Connector UL										
ITEM PN#	CORD LENGTH	WIRE GAUGE	WIRE TYPE	WIRE COLOR	OUTLETS	PLUG TYPE	RECEPTACLE TYPE	POWER RATING AMPS	WATTS	PACK QTY
04-00092	1ft	12/3	STW	Yellow	1	L5-30P	5-15R	15	1875	10



U-Ground Plug to Locking Connector UL										
ITEM PN#	CORD LENGTH	WIRE GAUGE	WIRE TYPE	WIRE COLOR	OUTLETS	PLUG TYPE	RECEPTACLE TYPE	POWER RATING AMPS	WATTS	PACK QTY
04-00093	1ft	12/3	STW	Yellow	1	5-15P	L5-20R	15	1875	10



20 Amp Generator "W" Adapter with Lighted Ends UL										
ITEM PN#	CORD LENGTH	WIRE GAUGE	WIRE TYPE	WIRE COLOR	OUTLETS	PLUG TYPE	RECEPTACLE TYPE	POWER RATING AMPS	WATTS	PACK QTY
04-00200	2ft	12/3	STW	Yellow	3	L5-20P	5-15R	15	1875	12



30 Amp Generator "W" Adapter with Lighted Ends UL										
ITEM PN#	CORD LENGTH	WIRE GAUGE	WIRE TYPE	WIRE COLOR	OUTLETS	PLUG TYPE	RECEPTACLE TYPE	POWER RATING AMPS	WATTS	PACK QTY
04-00201	2ft	12/3	STW	Yellow	3	L5-30P	5-15R	15	1875	12

Outdoor 300V SJTW Extension Cords -40°F TO 140°F

3-Conductor 300V SJTW Extension Cords



ITEM PN#	CORD LENGTH	WIRE GAUGE	WIRE TYPE	WIRE COLOR	OUTLETS	PLUG TYPE	RECEPTACLE TYPE	POWER RATING AMPS	WATTS	PACK QTY
05-00108	25ft	16/3	SJTW	Yellow	1	5-15P	5-15R	13	1625	12
05-00109	50ft	16/3	SJTW	Yellow	1	5-15P	5-15R	13	1625	12
05-00110	100ft	16/3	SJTW	Yellow	1	5-15P	5-15R	10	1250	6



3-Conductor 300V SJTW Extension Cords with Lighted End



ITEM PN#	CORD LENGTH	WIRE GAUGE	WIRE TYPE	WIRE COLOR	OUTLETS	PLUG TYPE	RECEPTACLE TYPE	POWER RATING AMPS	WATTS	PACK QTY
05-00341	25ft	14/3	SJTW	Orange/Black	1	5-15P	5-15R	15	1875	6
05-00342	50ft	14/3	SJTW	Orange/Black	1	5-15P	5-15R	15	1875	6
05-00343	100ft	14/3	SJTW	Orange/Black	1	5-15P	5-15R	13	1625	3
05-00364	25ft	12/3	SJTW	Yellow/Blue	1	5-15P	5-15R	15	1875	12
05-00365	50ft	12/3	SJTW	Yellow/Blue	1	5-15P	5-15R	15	1875	4
05-00366	100ft	12/3	SJTW	Yellow/Blue	1	5-15P	5-15R	15	1875	2
05-00350	50ft	10/3	SJTW	Yellow/Black	1	5-15P	5-15R	15	1875	1
05-00351	100ft	10/3	SJTW	Yellow/Black	1	5-15P	5-15R	15	1875	1



3-Conductor 300V SJTW Extension Cords with E-ZEELOCK™ and Lighted End



ITEM PN#	CORD LENGTH	WIRE GAUGE	WIRE TYPE	WIRE COLOR	OUTLETS	PLUG TYPE	RECEPTACLE TYPE	POWER RATING AMPS	WATTS	PACK QTY
05-00111	25ft	14/3	SJTW	Org/Blk	1	5-15P	5-15R	15	1875	6
05-00112	50ft	14/3	SJTW	Org/Blk	1	5-15P	5-15R	15	1875	6
05-00113	100ft	14/3	SJTW	Org/Blk	1	5-15P	5-15R	15	1875	3
05-00105	25ft	12/3	SJTW	Yell/Blu/Blu	1	5-15P	5-15R	15	1875	12
05-00106	50ft	12/3	SJTW	Yell/Blu/Blu	1	5-15P	5-15R	15	1875	4
05-00107	100ft	12/3	SJTW	Yell/Blu/Blu	1	5-15P	5-15R	15	1875	2

PRO SERIES product



OUTDOOR 300V EXTENSION CORDS

Outdoor 300V SJTW Extension Cords -40°F TO 140°F



3-Conductor 300V SJTW Extension Cord with Lighted Power Block



ITEM PN#	CORD LENGTH	WIRE GAUGE	WIRE TYPE	WIRE COLOR	OUTLETS	PLUG TYPE	RECEPTACLE TYPE	POWER RATING AMPS	WATTS	PACK QTY
05-00120	25ft	14/3	SJTW	Orange/Black	3	5-15P	5-15R	15	1875	12
05-00121	50ft	14/3	SJTW	Orange/Black	3	5-15P	5-15R	15	1875	6
05-00122	100ft	14/3	SJTW	Orange/Black	3	5-15P	5-15R	13	1625	4
05-00123	25ft	12/3	SJTW	Yellow/Blue	3	5-15P	5-15R	15	1875	8
05-00124	50ft	12/3	SJTW	Yellow/Blue	3	5-15P	5-15R	15	1875	4



3-Conductor 300V SJTW Extension Cord with Lighted Power Block



ITEM PN#	CORD LENGTH	WIRE GAUGE	WIRE TYPE	WIRE COLOR	OUTLETS	PLUG TYPE	RECEPTACLE TYPE	POWER RATING AMPS	WATTS	PACK QTY
05-00129	100ft	12/3	SJTW	Red	1	L5-20P	L5-20R	15	1875	2
05-00128	50ft	12/3	SJTW	Yellow/Blue	1	L5-20P	L5-20R	20	2500	4
05-00131	100ft	12/3	SJTW	Yellow/Blue	1	L5-20P	L5-20R	15	1875	2
05-00130	100ft	12/3	SJTW	Red/Black	1	L5-20P	L5-20R	15	1875	2




3-Conductor 300V SJTW Extension Cord with Quad Box



ITEM PN#	CORD LENGTH	WIRE GAUGE	WIRE TYPE	WIRE COLOR	OUTLETS	PLUG TYPE	RECEPTACLE TYPE	POWER RATING AMPS	WATTS	PACK QTY
11-00400	15ft	14/3	SJTW	Orange/Black	4	5-15P	5-15R	15	1875	6
11-00???										
11-00???										

OUTDOOR 300V EXTENSION CORDS





Why Voltec's SJEOW is Superior?



ALL-FLEX™ products are uncompromised and provide greater flexibility over a longer working life than most of the other products.

Voltec's ALL-FLEX™ SJEOW extension cords are made to withstand the most extreme conditions. With a temperature rating of -58°F to +221°F this cord can be used in freezing cold winters and sweltering hot summers. Our cords also resist the negative effects of oil, water, weather, abrasion and ozone, while providing a unit that weighs considerably less than rubber cords. **Our ALL-FLEX™** products are all cULus listed.



ALL-FLEX™ are available in 300V and 600V wire type in 16, 14, 12, and 10 gauge. Connector Ends include Power Block, Locking and E-ZEELock™

All Weather Outdoor 300V SJEOW Extension Cords -58°F TO 228°F

 3-Conductor 300V SJTW Extension Cords with Lighted End 										
ITEM PN#	CORD LENGTH	WIRE GAUGE	WIRE TYPE	WIRE COLOR	OUTLETS	PLUG TYPE	RECEPTACLE TYPE	POWER RATING AMPS	WATTS	PACK QTY
05-00134	15ft	16/3	SJEOW	Blue	1	5-15P	5-15R	13	1625	12
05-00135	25ft	16/3	SJEOW	Blue	1	5-15P	5-15R	13	1625	12
05-00136	50ft	16/3	SJEOW	Blue	1	5-15P	5-15R	13	1625	12
05-00137	100ft	16/3	SJEOW	Blue	1	5-15P	5-15R	10	1250	6
05-00361	25ft	14/3	SJEOW	Blue	1	5-15P	5-15R	15	1875	12
05-00362	50ft	14/3	SJEOW	Blue	1	5-15P	5-15R	13	1625	6
05-00363	100ft	14/3	SJEOW	Blue	1	5-15P	5-15R	13	1625	3
05-00358	25ft	12/3	SJEOW	Blue	1	5-15P	5-15R	15	1875	12
05-00359	50ft	12/3	SJEOW	Blue	1	5-15P	5-15R	15	1875	4
05-00360	100ft	12/3	SJEOW	Blue	1	5-15P	5-15R	15	1875	2
05-00356	50ft	10/3	SJEOW	Blue	1	5-15P	5-15R	15	1875	1
05-00357	100ft	10/3	SJEOW	Blue	1	5-15P	5-15R	15	1875	1





All Weather Outdoor 300V SJEOW Extension Cords -58°F to 228°

PRO SERIES product



3-Conductor 300V SJEOW Extension Cords with E-ZEELock™ and Lighted End cUL^{us}										
ITEM PN#	CORD LENGTH	WIRE GAUGE	WIRE TYPE	WIRE COLOR	OUTLETS	PLUG TYPE	RECEPTACLE TYPE	POWER RATING AMPS	WATTS	PACK QTY
05-00138	25ft	14/3	SJEOW	Blue	1	5-15P	5-15R	15	1875	6
05-00139	50ft	14/3	SJEOW	Blue	1	5-15P	5-15R	15	1875	6
05-00140	100ft	14/3	SJEOW	Blue	1	5-15P	5-15R	13	1625	3
05-00141	25ft	12/3	SJEOW	Blue	1	5-15P	5-15R	15	1875	12
05-00142	50ft	12/3	SJEOW	Blue	1	5-15P	5-15R	15	1875	4
05-00143	100ft	12/3	SJEOW	Blue	1	5-15P	5-15R	15	1875	2





3-Conductor 300V SJEOW Locking Extension Cords cUL^{us}										
ITEM PN#	CORD LENGTH	WIRE GAUGE	WIRE TYPE	WIRE COLOR	OUTLETS	PLUG TYPE	RECEPTACLE TYPE	POWER RATING AMPS	WATTS	PACK QTY
05-00231	100ft	12/3	SJEOW	Black	1	L5-20P	L5-20R	15	1875	2





3-Conductor 300V SJEOW Extension Cord with Power Block and Lighted End cUL^{us}										
ITEM PN#	CORD LENGTH	WIRE GAUGE	WIRE TYPE	WIRE COLOR	OUTLETS	PLUG TYPE	RECEPTACLE TYPE	POWER RATING AMPS	WATTS	PACK QTY
05-00147	25ft	12/3	SJEOW	Blue	3	5-15P	5-15R	15	1875	8
05-00148	50ft	12/3	SJEOW	Blue	3	5-15P	5-15R	15	1875	4
05-00148	100ft	12/3	SJEOW	Blue	3	5-15P	5-15R	15	1875	2

All Weather Outdoor 600V SEOW Extension Cords -58°F to 228°


 3-Conductor 600V SEOW Locking Extension Cord 										
ITEM PN#	CORD LENGTH	WIRE GAUGE	WIRE TYPE	WIRE COLOR	OUT-LETS	PLUG TYPE	RECEPTACLE TYPE	POWER RATING		PACK QTY
								AMPS	WATTS	
06-00231	100ft	12/3	SEOW	Black	1	L5-20P	L5-20R	15	1875	2




 3-Conductor 600V SEOW Locking Extension Cords 										
ITEM PN#	CORD LENGTH	WIRE GAUGE	WIRE TYPE	WIRE COLOR	OUT-LETS	PLUG TYPE	RECEPTACLE TYPE	POWER RATING		PACK QTY
								AMPS	WATTS	
06-00181	100ft	10/3	SEOW	Black	1	L6-30P	L6-30R	25	6250	1



Outdoor 600V STW Extension Cords -40°F to 140°

3-Conductor 300V STW Extension Cords 										
ITEM PN#	CORD LENGTH	WIRE GAUGE	WIRE TYPE	WIRE COLOR	OUTLETS	PLUG TYPE	RECEPTACLE TYPE	POWER RATING		PACK QTY
								AMPS	WATTS	
06-00162	50ft	12/3	STW	Yellow	1	5-15P	5-15R	15	1875	4
05-00163	100ft	12/3	STW	Yellow	1	5-15P	5-15R	15	1875	2



3-Conductor 300V STW Locking Extension Cords 										
ITEM PN#	CORD LENGTH	WIRE GAUGE	WIRE TYPE	WIRE COLOR	OUTLETS	PLUG TYPE	RECEPTACLE TYPE	POWER RATING		PACK QTY
								AMPS	WATTS	
06-00167	50ft	12/3	STW	Yellow	1	L5-20P	L5-20R	20	2500	4
06-00168	100ft	12/3	STW	Yellow	1	L5-20P	L5-20R	15	1875	2



Kwik Kustom 300V SJTW Extension Cords -40°F TO 140°F



3-Conductor 300V SJTW Color Extension Cords with Lighted End



ITEM PN#	CORD LENGTH	WIRE GAUGE	WIRE TYPE	WIRE COLOR	OUTLETS	PLUG TYPE	RECEPTACLE TYPE	POWER RATING		PACK QTY
								AMPS	WATTS	
05-00114	50ft	12/3	SJTW	FL Green/Black	1	5-15P	5-15R	15	1875	4
05-00116	100ft	12/3	SJTW	FL Green/Black	1	5-15P	5-15R	15	1875	2
05-00152	50ft	12/3	SJTW	Pink/Lime/Grn	1	5-15P	5-15R	15	1875	4
05-00153	100ft	12/3	SJTW	Pink/Lime/Grn	1	5-15P	5-15R	15	1875	2
05-00347	25ft	12/3	SJTW	Blue/Yellow	1	5-15P	5-15R	15	1875	12
05-00348	50ft	12/3	SJTW	Blue/Yellow	1	5-15P	5-15R	15	1875	4
05-00349	100ft	12/3	SJTW	Blue/Yellow	1	5-15P	5-15R	15	1875	2

For a different look. Available in stock.



Customized Cords

Customize to Benefit the Need

- ✓ Advertise your Company Name.
- ✓ Prevent Loss of cords from jobsite.
- ✓ Identify a color or stripe to a specific length and gauge.
- ✓ Provide a safe work area with high visibility colors.

Custom Colors

Choose from many of our custom colors.
Customize a color to meet your preference.

- ✓ Company Colors
- ✓ Personal Choice

Custom Striping

Clearly add identification to cords with striping.
The color and stripe combinations are endless.

- ✓ Single stripe
- ✓ DOUBLE stripe

Advertise with Custom ID

Keep cords on the jobsite. Personalize by advertising your company name and number on every extension cord. Choose from a standard indent wheel or ink printed.

- ✓ Company Name & Phone No.
- ✓ "Property of ABC"

Tailor Fit Your Need.

Choose your Plug and Connector End
Choose any of our standard plugs and receptacles to fit your exact need. Molded ends come in a variety of custom colors. The Choice is Yours!

Unique Features are an Option Too

- ✓ E-ZEELock™ Locking Connector - prevents annoying disconnects
- ✓ Illuminated Ends - timesaver, quickly shows you've got power.



Custom Order Quotes available online.
Go to www.voltec-industries.com

Kustom Order Quote

Distributor: _____ Prepared By: _____
Customer: _____ Date: _____



Quantity: _____ of 25ft
_____ of 50ft
_____ of 100ft
_____ of feet



Gauge: _____ 16/3
_____ 14/3
_____ 12/3
_____ 10/3



Cord Type:
_____ SJTW 300V
_____ SJE00W 300V
_____ STW 600V
_____ SEOW 600V

OPTIONS: (Circle Yes or No)
E-ZEELock®: Yes/No
GFCI: Yes/No


Choose Plug:


_____ NEMA 5-15P  




_____ NEMA L5-20P  

_____ NEMA 5-15P  

Choose Receptacle:

_____ NEMA 5-15R 

_____ NEMA L5-20R 

_____ NEMA 5-15R(3) 




Custom Imprinting: (Circle Yes or No)

Standard Indent: Yes/No Custom ink print: Yes/No
Custom ink print color code: _____

Custom Text: (maximum characters 125)
1 line:

Stripes and Colors:


No Stripe: _____ Single Stripe: _____ Double Stripe: _____ Stripe Color Code: _____
Cord Color Code: _____
Connector/Plug: Clear Lighted: Yes/No Color Code: _____



Above color chart is for reference only. Colors may not be exact match to cord color.

Adapters

Voltec's line of adapters for the professional trades includes 3-outlet power block, u-ground to locking and visa versa conversion adapters. "Y" and "W" adapters are also available in 15–20 amp configurations. All of these products are designed to maximize flexibility and are compatible with a variety of portable tools.

 3-Outlet Adapter with Lighted Power Block c UL US										
ITEM PN#	CORD LENGTH	WIRE GAUGE	WIRE TYPE	WIRE COLOR	OUTLETS	PLUG TYPE	RECEPTACLE TYPE	POWER RATING		PACK QTY
								AMPS	WATTS	
04-00089	2ft	12/3	SE00W	Blue	3	5-15P	5-15R	15	1875	6



3-Outlet Adapter with Lighted Power Block c UL US										
ITEM PN#	CORD LENGTH	WIRE GAUGE	WIRE TYPE	WIRE COLOR	OUTLETS	PLUG TYPE	RECEPTACLE TYPE	POWER RATING		PACK QTY
								AMPS	WATTS	
04-00088	1ft	14/3	SJTW	Orange/Black	3	5-15P	5-15R	15	1875	25
04-00090	2ft	12/3	STW	Yellow	3	5-15P	5-15R	15	1875	6



3-Outlet Adapter with Locking Plug and Lighted Power Block UL										
ITEM PN#	CORD LENGTH	WIRE GAUGE	WIRE TYPE	WIRE COLOR	OUTLETS	PLUG TYPE	RECEPTACLE TYPE	POWER RATING		PACK QTY
								AMPS	WATTS	
04-00091	2ft	12/3	STW	Yellow	3	L5-20P	5-15R	15	1875	6



U-Ground "Y" Adapter UL										
ITEM PN#	CORD LENGTH	WIRE GAUGE	WIRE TYPE	WIRE COLOR	OUTLETS	PLUG TYPE	RECEPTACLE TYPE	POWER RATING		PACK QTY
								AMPS	WATTS	
04-00094	2ft	12/3	STW	Yellow	2	5-15P	5-15R	15	1875	18



"Y" Adapter with Locking Plug and Lighted End UL										
ITEM PN#	CORD LENGTH	WIRE GAUGE	WIRE TYPE	WIRE COLOR	OUTLETS	PLUG TYPE	RECEPTACLE TYPE	POWER RATING		PACK QTY
								AMPS	WATTS	
04-00095	2ft	12/3	STW	Yellow	2	L5-20P	L5-20R	20	2500	18



U-Ground "W" Adapter UL										
ITEM PN#	CORD LENGTH	WIRE GAUGE	WIRE TYPE	WIRE COLOR	OUTLETS	PLUG TYPE	RECEPTACLE TYPE	POWER RATING		PACK QTY
								AMPS	WATTS	
04-00096	2ft	12/3	STW	Yellow	3	5-15P	5-15R	15	1875	12




"W" Adapter with Locking Plug and Lighted End UL										
ITEM PN#	CORD LENGTH	WIRE GAUGE	WIRE TYPE	WIRE COLOR	OUTLETS	PLUG TYPE	RECEPTACLE TYPE	POWER RATING		PACK QTY
								AMPS	WATTS	
04-00097	2ft	12/3	STW	Yellow	3	L5-20P	L5-20R	20	2500	12




Adapters

PRO SERIES product



E-ZEELOCK Locking Connector										
20 Amp Generator "W" Adapter with Lighted Ends UL										
ITEM PN#	CORD LENGTH	WIRE GAUGE	WIRE TYPE	WIRE COLOR	OUTLETS	PLUG TYPE	RECEPTACLE TYPE	POWER RATING AMPS	WATTS	PACK QTY
04-00200	2ft	12/3	STW	Yellow	3	L5-20P	5-15R	15	1875	12

PRO SERIES product



E-ZEELOCK Locking Connector										
30 Amp Generator "W" Adapter with Lighted Ends UL										
ITEM PN#	CORD LENGTH	WIRE GAUGE	WIRE TYPE	WIRE COLOR	OUTLETS	PLUG TYPE	RECEPTACLE TYPE	POWER RATING AMPS	WATTS	PACK QTY
04-00201	2ft	12/3	STW	Yellow	3	L5-30P	5-15R	15	1875	12



Locking Plug to U-Ground Connector UL										
ITEM PN#	CORD LENGTH	WIRE GAUGE	WIRE TYPE	WIRE COLOR	OUTLETS	PLUG TYPE	RECEPTACLE TYPE	POWER RATING AMPS	WATTS	PACK QTY
04-0092N	1ft	12/3	STW	Yellow	1	L5-20P	5-15R	20	2500	10

PRO SERIES product



E-ZEELOCK Locking Connector										
Locking Plug to U-Ground Connector UL										
ITEM PN#	CORD LENGTH	WIRE GAUGE	WIRE TYPE	WIRE COLOR	OUTLETS	PLUG TYPE	RECEPTACLE TYPE	POWER RATING AMPS	WATTS	PACK QTY
04-00092	1ft	12/3	STW	Yellow	1	L5-30P	5-15R	15	1875	10



U-Ground Plug to Locking Connector UL										
ITEM PN#	CORD LENGTH	WIRE GAUGE	WIRE TYPE	WIRE COLOR	OUTLETS	PLUG TYPE	RECEPTACLE TYPE	POWER RATING AMPS	WATTS	PACK QTY
04-0093N	1ft	12/3	STW	Yellow	1	5-15P	L5-20R	15	1875	10

PRO SERIES product



E-ZEELOCK Locking Connector										
U-Ground Plug to Locking Connector UL										
ITEM PN#	CORD LENGTH	WIRE GAUGE	WIRE TYPE	WIRE COLOR	OUTLETS	PLUG TYPE	RECEPTACLE TYPE	POWER RATING AMPS	WATTS	PACK QTY
04-00093	1ft	12/3	STW	Yellow	1	5-15P	L5-20R	15	1875	10



3-Outlet Wall Tap Adapters cUL us										
ITEM PN#	CORD LENGTH	WIRE GAUGE	WIRE TYPE	WIRE COLOR	OUTLETS	PLUG TYPE	RECEPTACLE TYPE	POWER RATING AMPS	WATTS	PACK QTY
04-00085				Clear with Light	3	5-15P	5-15R	15	1875	25
04-00087				Yellow	3	5-15P	5-15R	15	1875	25



Use your generator to its full potential. **Voltec's** line of heavy duty 10 and 12 AWG cords and adaptors allow you to fully utilize your 15amp and 20amp power tools. Our adaptor products will convert generator NEMA configurations to single, dual, triple and quad receptacle ends, while also converting 20/30 amp receptacles to locking, u-ground or **E-ZEELOCK®** versions.


20AMP Locking "Y" Adapter with Lighted Ends

ITEM PN#	CORD LENGTH	WIRE GAUGE	WIRE TYPE	WIRE COLOR	OUTLETS	PLUG TYPE	RECEPTACLE TYPE	POWER RATING AMPS	WATTS	PACK QTY
04-00095	2ft	12/3	STW	Yellow	2	L5-20P	L5-20R	20	2500	18



Locking "W" Adapter with Lighted Ends

ITEM PN#	CORD LENGTH	WIRE GAUGE	WIRE TYPE	WIRE COLOR	OUTLETS	PLUG TYPE	RECEPTACLE TYPE	POWER RATING AMPS	WATTS	PACK QTY
04-00097	2ft	12/3	STW	Yellow	3	L5-20P	L5-20R	20	2500	12



20 Amp Generator "W" Adapter with Lighted Ends


ITEM PN#	CORD LENGTH	WIRE GAUGE	WIRE TYPE	WIRE COLOR	OUTLETS	PLUG TYPE	RECEPTACLE TYPE	POWER RATING AMPS	WATTS	PACK QTY
04-00200	2ft	12/3	STW	Yellow	3	L5-20P	5-15R	15	1875	12



PRO SERIES product

30 Amp Generator "W" Adapter with Lighted Ends


ITEM PN#	CORD LENGTH	WIRE GAUGE	WIRE TYPE	WIRE COLOR	OUTLETS	PLUG TYPE	RECEPTACLE TYPE	POWER RATING AMPS	WATTS	PACK QTY
04-00201	2ft	12/3	STW	Yellow	3	L5-30P	5-15R	15	1875	12



PRO SERIES product


30AMP Locking "Y" Adapter with Lighted Ends

ITEM PN#	CORD LENGTH	WIRE GAUGE	WIRE TYPE	WIRE COLOR	OUTLETS	PLUG TYPE	RECEPTACLE TYPE	POWER RATING AMPS	WATTS	PACK QTY
04-00202	2ft	10/3	STW	Yellow	2	L5-30P	L5-20R	30	2500	4



20AMP Locking "Y" Adapter with Lighted Ends

ITEM PN#	CORD LENGTH	WIRE GAUGE	WIRE TYPE	WIRE COLOR	OUTLETS	PLUG TYPE	RECEPTACLE TYPE	POWER RATING AMPS	WATTS	PACK QTY
04-00203	2ft	10/4	STW	Blue/Yellow	2	L14-20P	5-20R	20	2500	4



30AMP Locking "Y" Adapter with Lighted Ends

ITEM PN#	CORD LENGTH	WIRE GAUGE	WIRE TYPE	WIRE COLOR	OUTLETS	PLUG TYPE	RECEPTACLE TYPE	POWER RATING AMPS	WATTS	PACK QTY
04-00204	2ft	10/4	STW	Blue/Yellow	2	L14-30P	5-20R	30	2500	4



30AMP Locking "Y" Adapter with Lighted Ends

ITEM PN#	CORD LENGTH	WIRE GAUGE	WIRE TYPE	WIRE COLOR	OUTLETS	PLUG TYPE	RECEPTACLE TYPE	POWER RATING AMPS	WATTS	PACK QTY
04-00205	2ft	10/4	STW	Blue/Yellow	2	L14-30P	5-20R	30	2500	4



30AMP Power Block with Lighted Ends

ITEM PN#	CORD LENGTH	WIRE GAUGE	WIRE TYPE	WIRE COLOR	OUTLETS	PLUG TYPE	RECEPTACLE TYPE	POWER RATING AMPS	WATTS	PACK QTY
04-00206	2ft	10/4	STW	Blue/Yellow	2	L14-30P	5-20R	20	2500	4



Generator Power Extension Cord



30AMP Locking Extension Cord with Lighted End

ITEM PN#	CORD LENGTH	WIRE GAUGE	WIRE TYPE	WIRE COLOR	OUTLETS	PLUG TYPE	RECEPTACLE TYPE	POWER RATING AMPS	WATTS	PACK QTY
04-00207	25ft	10/4	STW	Blue/Yellow	2	L14-30P	L14-30R	30	2500	1

PORTABLE GFCI

Ground Fault Circuit Interrupters

Voltec has a full line of portable GFCI adapters, including right angle and in-line configurations, to fit every application. Choose from both 15 Amp u-ground and 20 Amp locking configurations. GFCI's protect the user from an electrical shock resulting from an unequal flow of electricity caused by current leakage. The Occupational Safety and Health Administration (OSHA) regulations state "it is the employer's responsibility to provide GFCI's on all 120 volt, single phase, 15 and 20 Amp receptacles on job sites that are not part of the permanent wiring of the structure." All of Voltec's GFCI's meet or exceed all UL, cUL and OSHA requirements.



15AMP Portable GFCI

ITEM PN#	CORD LENGTH	WIRE GAUGE	WIRE TYPE	WIRE COLOR	OUTLETS	PLUG TYPE	RECEPTACLE TYPE	POWER RATING AMPS	WATTS	PACK QTY
11-00222	6ft	12/3	SJTW	Yellow/Blue	2	5-15P	5-15R	15	1875	6



15AMP GFCI Right Angle Adapter with Lighted Power Block

ITEM PN#	CORD LENGTH	WIRE GAUGE	WIRE TYPE	WIRE COLOR	OUTLETS	PLUG TYPE	RECEPTACLE TYPE	POWER RATING AMPS	WATTS	PACK QTY
04-00101	2ft	12/3	SJTW	Yellow/Blue	3	5-15P	5-15R	15	1875	6



15AMP GFCI Adapter with Lighted Power Block

ITEM PN#	CORD LENGTH	WIRE GAUGE	WIRE TYPE	WIRE COLOR	OUTLETS	PLUG TYPE	RECEPTACLE TYPE	POWER RATING AMPS	WATTS	PACK QTY
04-00105	2ft	12/3	SJTW	Yellow/Black	3	5-15P	5-15R	15	1875	6



20AMP GFCI Adapter with Lighted Power Block

ITEM PN#	CORD LENGTH	WIRE GAUGE	WIRE TYPE	WIRE COLOR	OUTLETS	PLUG TYPE	RECEPTACLE TYPE	POWER RATING AMPS	WATTS	PACK QTY
04-00102	3ft	12/3	SJTW	Yellow/Blue	3	5-15P	5-15R	15	1875	6



20AMP GFCI Adapter with Lighted End

ITEM PN#	CORD LENGTH	WIRE GAUGE	WIRE TYPE	WIRE COLOR	OUTLETS	PLUG TYPE	RECEPTACLE TYPE	POWER RATING AMPS	WATTS	PACK QTY
04-00103	3ft	12/3	STW	Yellow/Blue	1	5-15P	5-15R	15	1875	6



20AMP Locking GFCI

ITEM PN#	CORD LENGTH	WIRE GAUGE	WIRE TYPE	WIRE COLOR	OUTLETS	PLUG TYPE	RECEPTACLE TYPE	POWER RATING AMPS	WATTS	PACK QTY
04-00104	3ft	12/3	STW	Yellow/Blue	1	L5-20P	L5-20R	20	2500	6



Temporary Power

Voltec offers a variety of items for your temporary power needs. Applications include construction sites, entertainment industry, fairs, carnivals, party rental, and convention centers. We offer heavy-duty power cords featuring 50 Amp plugs and connectors. These temporary box units are cULus listed for use in wet and damp locations. Voltec Industries provides a repair facility in Chino, California.



Listed/UL 1640 / NEMA 3R
For Outdoor Use
Wet and Damp Locations

Temporary Power Box										
ITEM PN#	DESCRIPTION	POWER INLET	POWER OUTLET	GFCI	# GFCI	RECEPTACLES QTY TYPE		CIRCUIT BREAKER PROTECTED		PACK QTY
09-00375	Locking	50AMP 125/250V	50AMP 125/250V	Yes	3	6	L5-20R	Yes	Yes	1
				No		1	L6-30R	1		
09-00376	U-Ground	50AMP 125/250V	50AMP 125/250V	Yes	3	6	5-20R	Yes	Yes	1
				No		1	L6-30R	1		
09-00675	Locking	50AMP 125/250V	50AMP 125/250V	Yes	6	6	L5-20R	Yes	Yes	1
				No		1	L6-30R	1		
09-0T676	U-Ground	50AMP 125/250V	50AMP 125/250V	Yes	6	6	5-20R	Yes	Yes	1
				No		1	L6-30R	1		



"BIG-BLUE"



Temporary Vinyl Power Cords -40° to 140°F										
ITEM PN#	CORD LENGTH	WIRE GAUGE	WIRE TYPE	WIRE COLOR	OUTLETS	PLUG TYPE	RECEPTACLE TYPE	POWER RATING		PACK QTY
								AMPS	WATTS	
09-00214	50ft	6/3-8/1	STW	Black	1	50AMP	50AMP	50	12500	1
09-00215	100ft	6/3-8/1	STW	Black	1	50AMP	50AMP	50	10000	1



ALL-FLEX Temporary Rubber Power Cord -58° to 228°F										
ITEM PN#	CORD LENGTH	WIRE GAUGE	WIRE TYPE	WIRE COLOR	OUTLETS	PLUG TYPE	RECEPTACLE TYPE	POWER RATING		PACK QTY
								AMPS	WATTS	
09-00431	50ft	6/3-8/1	SOW	Black	1	50AMP	50AMP	50	12500	1
09-00432	100ft	6/3-8/1	SOW	Black	1	50AMP	50AMP	50	10000	1



Temporary "Y" Adapter -40° to 140°F										
ITEM PN#	CORD LENGTH	WIRE GAUGE	WIRE TYPE	WIRE COLOR	OUTLETS	PLUG TYPE	RECEPTACLE TYPE	POWER RATING		PACK QTY
								AMPS	WATTS	
09-00435	2ft	6/3-8/1	STW	Black	2	50AMP	50AMP	50	10000	1



Emergency Response STW Cord -40° to 140°F										
ITEM PN#	CORD LENGTH	WIRE GAUGE	WIRE TYPE	WIRE COLOR	OUTLETS	PLUG TYPE	RECEPTACLE TYPE	POWER RATING		PACK QTY
								AMPS	WATTS	
09-00436	2ft	6/3-8/1	STW	Black	2	14-50P	50AMP	50	10000	1

Temporary Lighting

Light Strings - **Voltec's** wide variety of light strings are the perfect solution to your temporary lighting needs at locations such as construction sites, parking lots, marinas and tree lots. Light strings are available in 50 or 100 ft lengths and are made with heavy-duty molded 150 watt sockets, which are spaced every ten feet. All of our light strings have pre-assembled plastic or metal cages which saves you time, as well as the cost of installation.



PRO SERIES product

U-Ground Light Strings with Plastic Cage

ITEM PN#	CORD LENGTH	WIRE GAUGE	WIRE TYPE	WIRE COLOR	BULB WATTS	OUTLETS	PLUG TYPE	RECEPTACLE TYPE	POWER RATING AMPS WATTS	PACK QTY
08-01187	50ft	14/3	SJTW	Yellow	150	5	1-15P	1-15R	15 1875	1
08-01188	100ft	14/3	SJTW	Yellow	150	10	1-15P	1-15R	15 1875	1
08-01189	50ft	12/3	SJTW	Yellow	150	5	5-15P	5-15R	15 1875	1
08-01190	100ft	12/3	SJTW	Yellow	150	10	5-15P	5-15R	15 1875	1
08-01193	50ft	12/3	STW	Yellow	150	5	5-15P	5-15R	15 1875	1
08-01194	100ft	12/3	STW	Yellow	150	10	5-15P	5-15R	15 1875	1



PRO SERIES product

Locking Light Strings with Plastic Cage

ITEM PN#	CORD LENGTH	WIRE GAUGE	WIRE TYPE	WIRE COLOR	BULB WATTS	OUTLETS	PLUG TYPE	RECEPTACLE TYPE	POWER RATING AMPS WATTS	PACK QTY
08-00192	100ft	12/3	SJTW	Yellow	150	10	L5-20P	L5-20R	20 2500	1

U-Ground Light Strings with Metal Cage

ITEM PN#	CORD LENGTH	WIRE GAUGE	WIRE TYPE	WIRE COLOR	BULB WATTS	OUTLETS	PLUG TYPE	RECEPTACLE TYPE	POWER RATING AMPS WATTS	PACK QTY
08-00197	50ft	12/3	SJTW	Yellow	150	5	5-15P	5-15R	15 1875	1
08-00198	100ft	12/3	SJTW	Yellow	150	10	5-15P	5-15R	15 1875	1
08-00199	50ft	12/3	STW	Yellow	150	5	5-15P	5-15R	15 1875	1
08-00200	100ft	12/3	STW	Yellow	150	10	5-15P	5-15R	15 1875	1

Locking Light Strings with Metal Cage

ITEM PN#	CORD LENGTH	WIRE GAUGE	WIRE TYPE	WIRE COLOR	BULB WATTS	OUTLETS	PLUG TYPE	RECEPTACLE TYPE	POWER RATING AMPS WATTS	PACK QTY
08-00202	100ft	12/3	STW	Yellow	150	10	L5-20P	L5-20R	20 2500	1

Light String Replacement Cages

ITEM PN#	DESCRIPTION	PACK QTY
08-00203	Plastic Cage for Light String	20
08-00204	Metal Cage for Light String	20



400 Metal Halide - Temporary Area Light

ITEM PN#	CORD LENGTH	WIRE GAUGE	WIRE TYPE	WIRE COLOR	BULB WATTS	OUTLETS	PLUG TYPE	RECEPTACLE TYPE	PACK QTY
08-00400	3ft	18/3	SJTW	Black	Clear Clamp 0	1	5-15P	5-15R	1

Replacement parts & bulbs available. See page 47.



Wiring Devices

Household Cords



3-Outlet 2 Conductor SPT-2 Extension Cords										
ITEM PN#	CORD LENGTH	WIRE GAUGE	WIRE TYPE	WIRE COLOR	OUTLETS	PLUG TYPE	RECEPTACLE TYPE	POWER RATING AMPS	WATTS	PACK QTY
01-00002	6ft	16/2	SPT-2	White	3	1-15P	1-15R	13	1625	25
01-00004	9ft	16/2	SPT-2	White	3	1-15P	1-15R	13	1625	25
01-00006	12ft	16/2	SPT-2	White	3	1-15P	1-15R	13	1625	25
01-00008	15ft	16/2	SPT-2	White	3	1-15P	1-15R	13	1625	25
01-00001	6ft	16/2	SPT-2	Brown	3	1-15P	1-15R	13	1625	25
01-00003	9ft	16/2	SPT-2	Brown	3	1-15P	1-15R	13	1625	25
01-00005	12ft	16/2	SPT-2	Brown	3	1-15P	1-15R	13	1625	25
01-00007	15ft	16/2	SPT-2	Brown	3	1-15P	1-15R	13	1625	25



3-Outlet 3 Conductor SPT-2 Extension Cords										
ITEM PN#	CORD LENGTH	WIRE GAUGE	WIRE TYPE	WIRE COLOR	OUTLETS	PLUG TYPE	RECEPTACLE TYPE	POWER RATING AMPS	WATTS	PACK QTY
01-00013	8ft	16/3	SPT-2	White	3	5-15P	5-15R	13	1625	25
01-00016	15ft	16/3	SPT-2	White	3	5-15P	5-15R	13	1625	25
01-00012	8ft	16/3	SPT-2	Brown	3	5-15P	5-15R	13	1625	25
01-00015	15ft	16/3	SPT-2	Brown	3	5-15P	5-15R	13	1625	25

Multiple Outlet Strips



6-Outlet Power Strip										
ITEM PN#	CORD LENGTH	WIRE GAUGE	WIRE TYPE	WIRE COLOR	OUTLETS	PLUG TYPE	RECEPTACLE TYPE	POWER RATING AMPS	WATTS	PACK QTY
11-00223	6ft	14/3	SJT	White	6	5-15P	5-15R	15	1875	12

6-Outlet Surge Power Strip										
ITEM PN#	CORD LENGTH	WIRE GAUGE	WIRE TYPE	WIRE COLOR	OUTLETS	PLUG TYPE	RECEPTACLE TYPE	POWER RATING AMPS	WATTS	PACK QTY
????	0ft	??/3	SJT	White	6	5-15P	5-15R	15	1875	12

Workbench Cords



3-Conductor Workbench SJTW Extension Cord										
ITEM PN#	CORD LENGTH	WIRE GAUGE	WIRE TYPE	WIRE COLOR	OUTLETS	PLUG TYPE	RECEPTACLE TYPE	POWER RATING AMPS	WATTS	PACK QTY
02-00034	10ft	16/3	SJTW	Black	1	5-15P	5-15R	13	1625	24



3-Outlet Workbench SJTW Extension Cord										
ITEM PN#	CORD LENGTH	WIRE GAUGE	WIRE TYPE	WIRE COLOR	OUTLETS	PLUG TYPE	RECEPTACLE TYPE	POWER RATING AMPS	WATTS	PACK QTY
02-00037	6ft	14/3	SJTW	Yellow/Blue	3	5-15P	5-15R	15	1875	12

Replacement Cords for Power Tools

Voltec's selection of power supply and replacement cords are compatible with most power tool and appliance manufacturers specifications. All of our power supply cords are UL listed with many carrying the cUL approval for Canada as well.

2 Conductor SJOW Repair Cord

ITEM PN#	CORD LENGTH	WIRE GAUGE	WIRE TYPE	WIRE COLOR	PLUG TYPE	POWER RATING AMPS WATTS	PACK QTY
03-00047	9ft	16/2	SJOW	Black	1-15P	13 1625	25
03-00447	50ft	16/2	SJOW	Black	1-15P	13 1625	6
03-00048	9ft	16/2	SJOW	Black	1-15P	13 1625	20



3 Conductor Locking SJTW Repair Cord

ITEM PN#	CORD LENGTH	WIRE GAUGE	WIRE TYPE	WIRE COLOR	PLUG TYPE	POWER RATING AMPS WATTS	PACK QTY
03-00059	50ft	16/3	SJTW	Black	L5-20P	13 1625	12



Rubber 3 Conductor SJ Repair Cords

ITEM PN#	CORD LENGTH	WIRE GAUGE	WIRE TYPE	WIRE COLOR	PLUG TYPE	POWER RATING AMPS WATTS	PACK QTY
03-00062	9ft	16/3	SJ	Black	5-15P	13 1625	25
03-00063	50ft	16/3	SJ	Black	5-15P	13 1625	6
03-00066	9	14/3	SJ	Black	5-15P	13 1625	24



Rubber 3 Conductor Locking SJ Repair Cords

ITEM PN#	CORD LENGTH	WIRE GAUGE	WIRE TYPE	WIRE COLOR	PLUG TYPE	POWER RATING AMPS WATTS	PACK QTY
03-00064	9ft	16/3	SJ	Black	L5-20P	13 1625	25
03-00065	50ft	16/3	SJ	Black	L5-20P	13 1625	6



Ranger and Dryer SRDT Cords

At **Voltec** we stock a full line of 3 wire SRDT cords manufactured with molded on right angle plugs. The 3 wire cords are required for homes built before 1996. Choose 3 wire cords for existing installation or replacement of damaged cords. Our 3 wire cords come standard with ring connectors, in your choice of plugs rated from 30–50 amps, and are available in 4 and 6-foot lengths.



3-Wire 30AMP 125/250V Dryer Cord Kits with Ring Terminals

ITEM PN#	CORD LENGTH	WIRE GAUGE	WIRE TYPE	WIRE COLOR	PLUG TYPE	RECEPTACLE TYPE	POWER RATING AMPS	WATTS	PACK QTY
03-00067	4ft	10/3	SRDT	Grey	10-30P	Ring Terminal	30	3750/7500	12
03-00069	6ft	10/3	SRDT	Grey	10-30P	Ring Terminal	30	3750/7500	12



3-Wire 40AMP 125/250V Range Cord Kits with Ring Terminals

ITEM PN#	CORD LENGTH	WIRE GAUGE	WIRE TYPE	WIRE COLOR	PLUG TYPE	RECEPTACLE TYPE	POWER RATING AMPS	WATTS	PACK QTY
03-00070	4ft	8/2-10/1	SRDT	Grey	10-50P	Ring Terminal	40	5000/10000	12
03-00072	6ft	8/2-10/1	SRDT	Grey	10-50P	Ring Terminal	40	5000/10000	12



3-Wire 50AMP 125/250V Range Cord Kits with Ring Terminals

ITEM PN#	CORD LENGTH	WIRE GAUGE	WIRE TYPE	WIRE COLOR	PLUG TYPE	RECEPTACLE TYPE	POWER RATING AMPS	WATTS	PACK QTY
03-00073	4ft	6/2-8/1	SRDT	Grey	10-50P	Ring Terminal	40	6250/12500	12
03-00075	6ft	6/2-8/1	SRDT	Grey	10-50P	Ring Terminal	40	6250/12500	12



4-Wire 30AMP 125/250V Dryer Cord Kits with Ring Terminals

ITEM PN#	CORD LENGTH	WIRE GAUGE	WIRE TYPE	WIRE COLOR	PLUG TYPE	RECEPTACLE TYPE	POWER RATING AMPS	WATTS	PACK QTY
03-00076	4ft	10/4	SRDT	Black	14-30P	Ring Terminal	30	3750/7500	12
03-00078	6ft	10/4	SRDT	Black	14-30P	Ring Terminal	30	3750/7500	12



4-Wire 40AMP 125/250V Range Cord Kits with Ring Terminals

ITEM PN#	CORD LENGTH	WIRE GAUGE	WIRE TYPE	WIRE COLOR	PLUG TYPE	RECEPTACLE TYPE	POWER RATING AMPS	WATTS	PACK QTY
03-00079	4ft	8/2-10/2	SRDT	Black	14-50P	Ring Terminal	40	5000/10000	12
03-00081	6ft	8/2-10/2	SRDT	Black	14-50P	Ring Terminal	40	5000/10000	12



4-Wire 50AMP 125/250V Range Cord Kits with Ring Terminals

ITEM PN#	CORD LENGTH	WIRE GAUGE	WIRE TYPE	WIRE COLOR	PLUG TYPE	RECEPTACLE TYPE	POWER RATING AMPS	WATTS	PACK QTY
03-00082	4ft	6/2-8/2	SRDT	Black	14-50P	Ring Terminal	50	6250/12500	12
03-00084	6ft	6/2-8/2	SRDT	Black	14-50P	Ring Terminal	50	6250/12500	12

Garbage Disposal/AC Power Supply Repair Cords

SPT-3 Replacement Cords

We recommend these power cords for use with electrical appliances such as garbage disposals and equipment with electrical motors that accept flat parallel wire. **Voltec's** repair cords are constructed with 3-conductor wire, and are provided to you with a choice of molded-on straight or right angle style plugs.

Heavy-Duty Power Supply Cords

Our heavy-duty power supply cords are made to replace used and worn out cords on most portable power tools. Available in 3-conductor, these cords feature molded plugs for added strength and durability. Choose from a selection of oil resistant, water resistant, or temperature resistant outer jacket compounds.

Air Conditioning/Major Appliance

3 Conductor Right Angle Plug Extension Cord									
ITEM PN#	CORD LENGTH	WIRE GAUGE	WIRE TYPE	WIRE COLOR	PLUG TYPE	RECEPTACLE TYPE	POWER RATING		PACK QTY
							AMPS	WATTS	
01-00040	6ft	14/3	SPT-3	Grey	5-15P	5-15R	15	1875	24
01-00041	9ft	14/3	SPT-3	Grey	5-15P	5-15R	15	1875	18
01-00042	12ft	14/3	SPT-3	Grey	5-15P	5-15R	15	1875	12
01-00043	15ft	14/3	SPT-3	Grey	5-15P	5-15R	15	1875	12



Garbage Disposal/Power Supply Cords

3 Conductor SPT-3 Repair Cords								
ITEM PN#	CORD LENGTH	WIRE GAUGE	WIRE TYPE	WIRE COLOR	PLUG TYPE	POWER RATING		PACK QTY
						AMPS	WATTS	
03-00049	3ft	16/3	SPT-3	Grey	5-15P	13	1625	25
03-00050	6ft	16/3	SPT-3	Grey	5-15P	13	1625	25
03-00051	8ft	16/3	SPT-3	Grey	5-15P	13	1625	25



3 Conductor Right Angle SPT-3 Replacement Cords								
ITEM PN#	CORD LENGTH	WIRE GAUGE	WIRE TYPE	WIRE COLOR	PLUG TYPE	POWER RATING		PACK QTY
						AMPS	WATTS	
03-00052	3ft	16/3	SPT-3	Grey	5-15P	13	1625	25
03-00053	4ft	16/3	SPT-3	Grey	5-15P	13	1625	25
03-00054	6ft	16/3	SPT-3	Grey	5-15P	13	1625	25
03-00055	8ft	16/3	SPT-3	Grey	5-15P	13	1625	25



Cord Reels

Open retractable cord reels assist in providing a well organized work area. They are available in numerous lengths and configurations for your exacting demands. Mounting hardware included.



3-Outlet Retractable Reel with Indoor Style Receptacles

ITEM PN#	REEL TYPE	CORD LENGTH	WIRE GAUGE	WIRE TYPE	WIRE COLOR	OUTLETS	PLUG TYPE	RECEPTACLE TYPE	POWER RATING AMPS	WATTS	PACK QTY
07-00282	2	30ft	16/3	SJTW	Yellow	3	5-15P	5-15R	10	1250	4

- Heavy Duty Metal Reel
- Resettable Circuit Breaker
- Mounting Hardware Included

PRO SERIES product



3-Outlet Retractable Reels with Outdoor Style Receptacles

ITEM PN#	REEL TYPE	CORD LENGTH	WIRE GAUGE	WIRE TYPE	WIRE COLOR	OUTLETS	PLUG TYPE	RECEPTACLE TYPE	POWER RATING AMPS	WATTS	PACK QTY
07-00283	3	50ft	14/3	SJTW	Yellow	3	5-15P	5-15R	13	1625	2
07-00284	3	50ft	12/3	SJTW	Yellow	3	5-15P	5-15R	15	1875	2

- 3-Way Wall/Ceiling/Bench Mount
- Mounting Hardware Included
- 5-Locking Positions
- 3-Outlet Power Block
- Convenient Carry Handle
- Resettable Circuit Breaker



4-Outlet Open Cord Reel

ITEM PN#	REEL TYPE	CORD LENGTH	WIRE GAUGE	WIRE TYPE	WIRE COLOR	OUTLETS	PLUG TYPE	RECEPTACLE TYPE	POWER RATING AMPS	WATTS	PACK QTY
07-00173	4	20ft	16/3	SJTW	Yellow	4	5-15P	5-15R	10	1250	2

- Resettable Circuit Breaker
- Convenient Carry Handle



4-Outlet Open Cord Reel with Stand

ITEM PN#	REEL TYPE	CORD LENGTH	WIRE GAUGE	WIRE TYPE	WIRE COLOR	OUTLETS	PLUG TYPE	RECEPTACLE TYPE	POWER RATING AMPS	WATTS	PACK QTY
07-00405	4	25ft	16/3	SJTW	Yellow	3	5-15P	5-15R	10	1250	4
07-00403	4	40ft	16/3	SJTW	Yellow	4	5-15P	5-15R	10	1250	2

- Resettable Circuit Breaker
- LED Power Indicator
- Sturdy, Durable Stand
- Convenient Easy Grip Handle

Clamp Lighting

Multi-use utility lamps with polished and vented aluminum reflectors. Units feature double universal joints, non-marring grips, clamp on brackets, on/off push-through switch and molded plugs.

5 1/2" Aluminum Reflector Clamp Lamp

ITEM PN#	CORD LENGTH	WIRE GAUGE	WIRE TYPE	WIRE COLOR	BULB WATTS	PLUG TYPE	PACK QTY
08-00177	6ft	18/2	SPT-2	Black	100	1-15P	4



8 1/2" Aluminum Reflector Clamp Lamp

ITEM PN#	CORD LENGTH	WIRE GAUGE	WIRE TYPE	WIRE COLOR	BULB WATTS	PLUG TYPE	PACK QTY
08-00178	6ft	18/2	SPT-2	Black	100	1-15P	4



10" Aluminum Reflector Clamp Lamp

ITEM PN#	CORD LENGTH	WIRE GAUGE	WIRE TYPE	WIRE COLOR	BULB WATTS	PLUG TYPE	PACK QTY
08-00179	6ft	18/2	SPT-2	Black	100	1-15P	4



Wire Cage Clamp Lamp

ITEM PN#	CORD LENGTH	WIRE GAUGE	WIRE TYPE	WIRE COLOR	BULB WATTS	PLUG TYPE	PACK QTY
08-00346	6ft	18/2	SPT-2	Black	150	1-15P	4

Brooder Lamp

ITEM PN#	CORD LENGTH	WIRE GAUGE	WIRE TYPE	WIRE COLOR	BULB WATTS	PLUG TYPE	PACK QTY
08-00433	6ft	18/2	SPT-2	Black	250	1-15P	4

- 250 Watt "A" Bulb capacity
- Polished Aluminum Reflector
- Convenient Hanging Hook



Brooder Lamp with Clamp and Hook

ITEM PN#	CORD LENGTH	WIRE GAUGE	WIRE TYPE	WIRE COLOR	BULB WATTS	PLUG TYPE	PACK QTY
08-00032	6ft	18/2	SPT-2	Black	250	1-15P	4

- 250 Watt "A" Bulb capacity
- Heavy Duty Clamp and Hook
- Polished Aluminum Reflector
- Convenient Hanging Hook

PRO SERIES product



Incandescent Work Lights

Voltec incandescent worklights provide durability and practicality. Constructed from tough PVC, these lights can withstand the rigors of a tough work environment.



12V Plastic Shade Work Light with Battery Clips

ITEM PN#	CORD LENGTH	WIRE GAUGE	WIRE TYPE	WIRE COLOR	BULB WATTS	PLUG TYPE	PACK QTY
08-00255	20ft	18/2	SPT-1	Yellow	60	Clips	6



Plastic Shade Work Lights

ITEM PN#	CORD LENGTH	WIRE GAUGE	WIRE TYPE	WIRE COLOR	BULB WATTS	PLUG TYPE	PACK QTY
08-00256	6ft	18/2	SJT	Yellow	75	1-15P	4
08-00181	25ft	18/2	SJT	Yellow	75	1-15P	10



Metal Shade Work Light with Outlet in Handle

ITEM PN#	CORD LENGTH	WIRE GAUGE	WIRE TYPE	WIRE COLOR	OUTLETS	PLUG TYPE	RECEPTACLE TYPE	BULB RATING	PACK QTY
08-00257	25ft	18/3	SJT	Yellow	1	5-15P	5-15R	75	6
08-00258	50ft	18/3	SJT	Yellow	1	5-15P	5-15R	75	6
08-00183	6ft	16/3	SJT	Yellow	1	5-15P	5-15R	75	4
08-00184	25ft	16/3	SJT	Yellow	1	5-15P	5-15R	75	4
08-00185	50ft	16/3	SJT	Yellow	1	5-15P	5-15R	75	6

PRO SERIES product



Industrial Metal Shade Work Light with Outlet in Handle

ITEM PN#	CORD LENGTH	WIRE GAUGE	WIRE TYPE	WIRE COLOR	OUTLETS	PLUG TYPE	RECEPTACLE TYPE	BULB RATING	PACK QTY
08-00186	25ft	16/3	SJT	Yellow	1	5-15P	5-15R	100	6
08-00382	25ft	12/3	SJTW	Yellow	1	5-15P	5-15R	100	6
08-00259	25ft	16/3	SJTOW	Yellow	1	5-15P	5-15R	100	6

Incandescent Trouble Lights with Retractable Reel

Voltec's incandescent retractable reels are constructed of tough ABS or heavy duty steel and mount easily for use in any work environment. Mounting hardware included.

Magnetic Utility Power Light Reel

ITEM PN#	CORD LENGTH	WIRE GAUGE	WIRE TYPE	WIRE COLOR	BULB WATTS	PLUG TYPE	PACK QTY
08-00275	10ft	18/2	SPT-2	Black	10	12V DC	10



Metal Guard Work Light Retractable Reel

ITEM PN#	REEL TYPE	CORD LENGTH	WIRE GAUGE	WIRE TYPE	WIRE COLOR	OUTLETS	BULB RATING	PLUG TYPE	RECEPTACLE TYPE	POWER RATING AMPS	WATTS	PACK QTY
07-00252	1	20ft	18/3	SVT	Yellow	1	75	5-15P	5-15R	7	875	4

- Grounded Outlet in Handle
- Durable Metal Guard
- Resettable Circuit Breaker
- High Visibility Cord Color



Metal Guard Work Light Retractable Reel with Outlet in Handle

ITEM PN#	REEL TYPE	CORD LENGTH	WIRE GAUGE	WIRE TYPE	WIRE COLOR	OUTLETS	BULB RATING	PLUG TYPE	RECEPTACLE TYPE	POWER RATING AMPS	WATTS	PACK QTY
07-00176	2	50ft	18/3	SVT	Yellow	1	75	5-15P	5-15R	6	750	4
07-00253	2	35ft	16/3	SJTW	Yellow	1	75	5-15P	5-15R	10	1250	4

- Grounded Outlet in Handle
- Durable Metal Guard
- Resettable Circuit Breaker
- High Visibility Cord Color



Industrial Metal Guard Work Light Retractable Reel with Outlet in Handle

ITEM PN#	REEL TYPE	CORD LENGTH	WIRE GAUGE	WIRE TYPE	WIRE COLOR	OUTLETS	BULB RATING	PLUG TYPE	RECEPTACLE TYPE	POWER RATING AMPS	WATTS	PACK QTY
07-00254	3	50ft	16/3	SJTW	Yellow	1	75	5-15P	5-15R	13	1625	2

- Grounded Outlet in Handle
- Durable Metal Guard
- Resettable Circuit Breaker
- High Visibility Cord Color



PRO SERIES product



Replacement parts & bulbs available. See page 47.



E-ZEE LAMP

Makes Bulb Replacement Easy

VOLTEC'S Full line of patented E-ZEE Lamp Fluorescent Products make bulb replacement simple. No more splitting the case or removing the handle base, simply remove the lens and easily replace the bulb.

Voltec's high quality lights are made from tough, rugged plastic. They feature dual hanging hooks, protective bumper guards, and an ergonomically designed handle.

Voltec's E-Zee Lamp design is also available on our retractable reels.

- E-ZEE LAMP BULB REPLACEMENT
- PATENTED BULB RATCHETING DESIGN
- HIGH QUALITY LIGHTS
- DUAL HANGING HOOKS
- PROTECTIVE BUMPER GUARDS
- ERGONOMICAL HANDLES

STEP 1



Take off lens by removing side screws

STEP 2



Pull bulbs effortlessly forward to a 30° angle and remove top silicon bulb holder

STEP 3



Easily remove old bulb and replace with new bulb. Replace top bulb holder, push bulbs back in the case and close lens to finish!

Economy Fluorescent Work Lights

Fluorescent – Cold to the touch and energy efficient, our fluorescent work lights come in 13 and 26-watt tube and angle styles. The units are equipped with SVT, SJT, and SJTW cords. These lights are available with 2 and 3-conductor plugs. Some lights are also available with 3-conductor grounding outlets in the handles. All lights utilize a standard 13-watt compact fluorescent bulb, which is included with each fixture, (the 26 watt accepts two 13 watt bulbs). Our fluorescent work lights are UL and cUL approved.

13 Watt Compact Fluorescent Tube Lights

ITEM PN#	CORD LENGTH	WIRE GAUGE	WIRE TYPE	WIRE COLOR	BULB WATTS	PLUG TYPE	PACK QTY
08-00263	6ft	18/2	SJT	Yellow	13	1-15P	6
08-00264	25ft	18/2	SJT	Yellow	13	1-15P	6



15 Watt Fluorescent Tube Lights

ITEM PN#	CORD LENGTH	WIRE GAUGE	WIRE TYPE	WIRE COLOR	BULB WATTS	PLUG TYPE	PACK QTY
08-00266	25ft	18/2	SJT	Yellow	15	1-15P	6

Professional Fluorescent Worklights



Designed to provide maximum lighting for the working professional. A durable compact casing to maneuver into the most tighest of spots. Ergonomic handle makes it quite comfortable for lengthy hold times. Hang light using one of the dual rotating hooks positioned on either end gaining all-way positioning.

13 Watt Compact Fluorescent Angle Light with No Switch

ITEM PN#	CORD LENGTH	WIRE GAUGE	WIRE TYPE	WIRE COLOR	BULB WATTS	PLUG TYPE	PACK QTY
08-00267	25ft	18/2	SJT	Yellow	13	1-15P	6

- OSHA Recognized
- E-ZEE Lamp Replacement



13 Watt Compact Fluorescent Angle Light with Outlet in Handle

ITEM PN#	CORD LENGTH	WIRE GAUGE	WIRE TYPE	WIRE COLOR	OUTLETS	PLUG TYPE	RECEPTACLE TYPE	BULB RATING	PACK QTY
08-00207	6ft	16/3	SJT	Yellow	1	5-15P	5-15R	13	4
08-00268	25ft	16/3	SJT	Yellow	1	5-15P	5-15R	13	6

- E-ZEE Lamp Replacement



26 Watt Electronic Compact Fluorescent Angle Light with Outlet in Handle

ITEM PN#	CORD LENGTH	WIRE GAUGE	WIRE TYPE	WIRE COLOR	OUTLETS	PLUG TYPE	RECEPTACLE TYPE	BULB RATING	PACK QTY
08-00208	6ft	16/3	SJT	Yellow	1	5-15P	5-15R	26 (2x13)	4
08-00270	25ft	16/3	SJT	Yellow	1	5-15P	5-15R	26 (2x13)	6
08-00270	50ft	16/3	SJT	Yellow	1	5-15P	5-15R	26 (2x13)	4

- E-ZEE Lamp Replacement



Replacement parts & bulbs available. See page 47.

Fluorescent Retractable Reels

Voltec's fluorescent retractable reels are constructed of tough ABS or heavy duty steel and mount easily for use in any work environment. Mounting hardware included.



13 Watt Compact Fluorescent Tube Light Retractable Reel

ITEM PN#	REEL TYPE	CORD LENGTH	WIRE GAUGE	WIRE TYPE	WIRE COLOR	BULB RATING	PLUG TYPE	RECEPTACLE TYPE	PACK QTY
07-00246	1	20ft	18/2	SVT	Yellow	13w	5-15P	5-15R	4



13 Watt Compact Fluorescent Tube Light Retractable Reel

ITEM PN#	REEL TYPE	CORD LENGTH	WIRE GAUGE	WIRE TYPE	WIRE COLOR	BULB RATING	PLUG TYPE	RECEPTACLE TYPE	POWER RATING AMPS	WATTS	PACK QTY
07-00248	2	50ft	18/2	SVT	Yellow	13w	5-15P	5-15R	10	1250	4



13 Watt Fluorescent Angle Retractable Reel with Magnet and Outlet in Handle

ITEM PN#	REEL TYPE	CORD LENGTH	WIRE GAUGE	WIRE TYPE	WIRE COLOR	OUTLETS	BULB RATING	PLUG TYPE	RECEPTACLE TYPE	POWER RATING AMPS	WATTS	PACK QTY
07-00249	2	50ft	16/3	SJTW	Yellow	1	13w	5-15P	5-15R	10	1250	2

- E-ZEE Lamp Replacement

PRO SERIES product



13W Fluorescent Mountable Retractable Reel with Magnet and Outlet in Handle

ITEM PN#	REEL TYPE	CORD LENGTH	WIRE GAUGE	WIRE TYPE	WIRE COLOR	OUTLETS	BULB RATING	PLUG TYPE	RECEPTACLE TYPE	POWER RATING AMPS	WATTS	PACK QTY
07-00250	2	50ft	16/3	SJTW	Yellow	1	13w	5-15P	5-15R	10	1250	2

- 5 Locking Positions
- 3-Way Wall/Ceiling/Bench Mount
- Mounting Hardware Included
- E-ZEE Lamp Replacement
- Convenient Carry Handle
- Resettable Circuit Breaker



26W Fluorescent Mountable Retractable Reel with Magnet and Outlet in Handle

ITEM PN#	REEL TYPE	CORD LENGTH	WIRE GAUGE	WIRE TYPE	WIRE COLOR	OUTLETS	BULB RATING	PLUG TYPE	RECEPTACLE TYPE	POWER RATING AMPS	WATTS	PACK QTY
07-00251	3	50ft	16/3	SJTW	Yellow	1	26w	5-15P	5-15R	10	1250	2

- 5 Locking Positions
- 3-Way Wall/Ceiling/Bench Mount
- Mounting Hardware Included
- E-ZEE Lamp Replacement
- Convenient Carry Handle
- Resettable Circuit Breaker

Replacement parts & bulbs available. See page 47.

Halogen Work Lights

Economy Halogen Work Lights

Halogen Portable Work Lights

ITEM PN#	MAX WATTAGE	CORD LENGTH	WIRE GAUGE	WIRE TYPE	WIRE COLOR	PLUG TYPE	SWITCH	PACK QTY
08-00212	250	1ft	18/3	SJTW	Black	5-15P	No	4
08-00209	500	3ft	18/3	SJTW	Black	5-15P	No	6

- S-Style Base
- Insulated Foam Handles
- Bulb(s) Included



Halogen Portable Work Light with Locking Plug

ITEM PN#	MAX WATTAGE	CORD LENGTH	WIRE GAUGE	WIRE TYPE	WIRE COLOR	PLUG TYPE	SWITCH	PACK QTY
08-00219	500	3ft	16/3	SJTW	Black	L5-20P	No	6

- S-Style Base
- Insulated Foam Handles
- Bulb(s) Included



Halogen Clamp Lamp

ITEM PN#	MAX WATTAGE	CORD LENGTH	WIRE GAUGE	WIRE TYPE	WIRE COLOR	PLUG TYPE	SWITCH	PACK QTY
08-00610	250	3ft	18/3	SJTW	Black	5-15P	Yes	6

- S-Style Base
- Hook, Clamp, and Stake Option
- Bulb(s) Included



Halogen Tripod Work Lights

ITEM PN#	MAX WATTAGE	CORD LENGTH	WIRE GAUGE	WIRE TYPE	WIRE COLOR	PLUG TYPE	SWITCH	PACK QTY
08-00211	1000	5ft	18/3	SJTW	Black	5-15P	Yes	2

- Tripod Extends to 5 feet
- Bulb(s) Included



Halogen Work Lights

Voltec Halogen Work Lights

Halogen Portable Work Light

ITEM PN#	MAX WATTAGE	CORD LENGTH	WIRE GAUGE	WIRE TYPE	WIRE COLOR	PLUG TYPE	SWITCH	PACK QTY
08-00609	500	3ft	18/3	SJTW	Black	5-15P	Yes	6

- H-Base Design
- Heavy Duty Face Frames
- Insulated Foam Handles
- Bulb(s) Included

Optional Base Magnet for Select Models

08-00314	Single Halogen Base Magnet
----------	----------------------------

Halogen Tripod Work Lights

ITEM PN#	MAX WATTAGE	CORD LENGTH	WIRE GAUGE	WIRE TYPE	WIRE COLOR	PLUG TYPE	SWITCH	PACK QTY
08-00210	500	5ft	18/3	SJTW	Black	5-15P	Yes	2
08-00611	1000	5ft	18/3	SJTW	Black	5-15P	Yes	2

- Tripod Extends to 6 feet
- Tripod Features 2 in 1 Removable H-Base
- H-Base Design
- Heavy Duty Face Frames
- Insulated Foam Handles
- Bulb(s) Included

Halogen Portable Work Lights

ITEM PN#	MAX WATTAGE	CORD LENGTH	WIRE GAUGE	WIRE TYPE	WIRE COLOR	PLUG TYPE	SWITCH	PACK QTY
08-00613	600	5ft	18/3	SJTW	Black	5-15P	Yes	2
08-00615	700	5ft	18/3	SJTW	Black	5-15P	Yes	2

- Heavy Duty H-Base Design
- Heavy Duty Face Frames
- Heavy Duty Grill
- Insulated Foam Handles
- Larger Housing for Higher Wattage
- Bulb(s) Included




Halogen Tripod Work Lights

ITEM PN#	MAX WATTAGE	CORD LENGTH	WIRE GAUGE	WIRE TYPE	WIRE COLOR	PLUG TYPE	SWITCH	PACK QTY
08-00614	1200	7ft	18/3	SJTW	Black	5-15P	Yes	2
08-00616	1400	7ft	18/3	SJTW	Black	5-15P	Yes	2

- Tripod Extends to 7 feet
- Tripod Features 2 in 1 Removable H-Base
- Heavy Duty H-Base Design
- Heavy Duty Face Frames
- Heavy Duty Grill
- Insulated Foam Handles
- Larger Housing for Higher Wattage
- Bulb(s) Included

Replacement parts & bulbs available. See page 47.



Voltec-Pro Work Lights

Energy Saving Work Lights

PRO SERIES product

Portable Work Lights

ITEM PN#	MAX WATTAGE	CORD LENGTH	WIRE GAUGE	WIRE TYPE	WIRE COLOR	PLUG TYPE	SWITCH	PACK QTY	
08-00701	65	5ft	18/3	SJTW	Black	5-15P	Yes	4	
08-00703	LED	Rechargeable				Black	5-15P	Yes	6


- Heavy Duty H-Base Design
- Heavy Duty Face Frames
- Low Heat Output
- Bright White Light Output
- Insulated Foam Handles
- Bulb(s) Included



Fluorescent Tripod Work Light

ITEM PN#	MAX WATTAGE	CORD LENGTH	WIRE GAUGE	WIRE TYPE	WIRE COLOR	PLUG TYPE	SWITCH	PACK QTY
08-00702	65	5ft	18/3	SJTW	Black	5-15P	Yes	2

- Tripod Extends to 7 feet
- Tripod Features 2 in 1 Removable H-Base
- Heavy Duty H-Base Design
- Heavy Duty Face Frames
- Low Heat Output
- Bright White Light Output
- Insulated Foam Handles
- Bulb(s) Included



Voltec-Pro LED Lights Made with Military Aerospace Grade Aluminum Body

LED Torch Light with Wrist Strap

ITEM PN#	TOTAL LED	LUMENS	BATTERY TYPE	RUN TIME	CHARGE TIME	AC	DC	TRAY PACK QTY
08-00696	9	45	3 AAA	7hrs	N/A	No	No	12





Hands-Free LED Head Lamp

ITEM PN#	TOTAL LED	LUMENS	BATTERY TYPE	RUN TIME	CHARGE TIME	AC	DC	TRAY PACK QTY
08-00697	14	75	3 AAA	7hrs	N/A	No	No	12



LED Light with Belt Holster

ITEM PN#	TOTAL LED	LUMENS	BATTERY TYPE	RUN TIME	CHARGE TIME	AC	DC	PACK QTY
08-00698	16 + 1/W	96 + 100	3 AAA	7hrs	N/A	No	No	6



Rechargeable LED Light with Recessed Magnet and AC & DC Chargers

ITEM PN#	TOTAL LED	LUMENS	BATTERY TYPE	RUN TIME	CHARGE TIME	AC	DC	PACK QTY
08-00699	30 + 1/W	180 + 100	7.2v NIMH	3.5hrs	4hrs	Yes	Yes	6
08-00700	60 + 1/W	360 + 100	7.2v NIMH	3.0hrs	4hrs	Yes	Yes	6

- Made with Military Aerospace Grade Aluminum Body

Rubber Booster Cables

Voltec offers a full line of durable rubber booster cables. These cables are resistant to extreme temperatures, oil and chemicals. They are available in medium-duty 10 and 8 AWG as well as heavy-duty 6 and 4 AWG, and extra-heavy duty 2 AWG. We offer these in a variety of lengths to match every need.



Bi-Metal Booster Cables							
ITEM PN#	GAUGE	CORD LENGTH	WIRE TYPE	WIRE COLOR	CLAMP TYPE	POWER AMPS	PACK QTY
10-00224	10	12ft	Rubber	Red/Black	Light Duty Clamp		6
10-00273	8	12ft	Rubber	Yellow/Black	Med Duty Side/Top Clamp		6
10-00305	6	12ft	Rubber	Orange/Black	Med Duty Side/Top Clamp		6
10-00275	6	16ft	Rubber	Orange/Black	Med Duty Side/Top Clamp		6
10-00307	4	16ft	Rubber	Blue/Black	Med Duty Side/Top Clamp		6
10-00320	1	25ft	Rubber	Red/Black	Hvy Duty Industrial Clamp		2



Copper Booster Cables PRO SERIES product							
ITEM PN#	GAUGE	CORD LENGTH	WIRE TYPE	WIRE COLOR	CLAMP TYPE	POWER AMPS	PACK QTY
10-00277	4	20ft	Rubber	Blue/Black	Heavy Duty Parrot Jaw Clamp	500	6
10-00276	2	20ft	Rubber	Blue/Black	Heavy Duty Parrot Jaw Clamp	500	6



PRO SERIES product



PRO SERIES product



Replacement Booster Clamps				
ITEM PN#	CORD LENGTH	CLAMP TYPE	POWER AMPS	PACK QTY
10-00372	250Amp Clamp (Pair)	Light Duty Clamp	50	12
10-00301	400Amp Clamp (Pair)	Med Duty Side/Top Clamp	400	12
10-00302	500Amp Clamp (Pair)	Hvy Duty Parrot Jaw Clamp	500	12
10-00303	800Amp Clamp (Pair)	Hvy Duty Industrial Clamp	800	12



Jump Starts and Power Packs

Voltec portable booster power packs are a safe and easy way to jump start your car, truck, boat or RV. They provide the ultimate in convenience for power failures, emergencies and road side assistance.

Jump Start Booster Packs

ITEM PN#	BATTERY	PEAK AMPS	CABLE TYPE	CABLE LENGTH	AIR COMPRESSOR	INVERTER	USB FEATURE	PACK QTY
10-00455	7AH	400	8G CCA	18"	No	No	Yes	1
10-00456	12AH	750	6G CCA	18"	No	No	Yes	1
10-00457	17AH	1700	6G CCA	28"	No	No	Yes	1
10-00458	22AH	2200	4G CCA	28"	120PSI	No	Yes	1

- Bullet points
- Bullet points
- Bullet points
- Bullet points



10-00455



10-00456



10-00457



10-00458



10-00458

Jump Start Booster Packs

ITEM PN#	BATTERY	PEAK AMPS	CABLE TYPE	CABLE LENGTH	AIR COMPRESSOR	INVERTER	USB FEATURE	PACK QTY
10-00459	2X22AH	3400	4G PURE	48"	No	No	Yes	1

- Bullet Points
- Bullet Points
- Bullet Points

PRO SERIES product



Power Pack - All In One

ITEM PN#	BATTERY	PEAK AMPS	CABLE TYPE	CABLE LENGTH	AIR COMPRESSOR	INVERTER	USB FEATURE	PACK QTY
10-00460	12AH	1200	6G CCA	34"	No	300W	No	1

- Reverse Alarm
- Color Coded Volt Meter Indicates Battery Status
- Fully Automatic with Floating Charge
- 2 each 12V Power Outlet in Front Panel
- Short Circuit Protection
- On/Off Switch
- Super-Bright LED Work Light



Optional Trolley Cart

ITEM PN#	DESCRIPTION	PACK QTY
10-00454	Trolley Cart for Jump Starts and Power Pack	1

- Heavy Duty Steel Construction
- Adjustable for Custom Fit



Power Inverters

Voltec power inverters provide instant 115/120 volt AC power from your car, truck, boat, SUV or RV. Models range from 100W to 3000W for a varied range of applications. Designed for safety, durability and reliability.



100W Power Inverter with Swivel Plug

ITEM PN#	MAX CONTINUOUS POWER	PEAK POWER	USB PORT	AC OUTLETS	REMOTE CONTROL	PACK QTY
10-00474	100W	200W	1	1	N/A	4



400W Power Inverter

ITEM PN#	MAX CONTINUOUS POWER	PEAK POWER	USB PORT	AC OUTLETS	REMOTE CONTROL	PACK QTY
10-00477	400W	800W	1	2	N/A	4



750W Power Inverter

ITEM PN#	MAX CONTINUOUS POWER	PEAK POWER	USB PORT	AC OUTLETS	REMOTE CONTROL	PACK QTY
10-00479	750W	1500W	1	2	N/A	4



1000W Power Inverter (cables sold separately)

ITEM PN#	MAX CONTINUOUS POWER	PEAK POWER	USB PORT	AC OUTLETS	REMOTE CONTROL	PACK QTY
10-00480	1000W	2000W	1	2	Yes	2



1500W Power Inverter (cables sold separately)

ITEM PN#	MAX CONTINUOUS POWER	PEAK POWER	USB PORT	AC OUTLETS	REMOTE CONTROL	PACK QTY
10-00481	1500W	3000W	1	2	Yes	2



2000W Power Inverter (cables sold separately)

ITEM PN#	MAX CONTINUOUS POWER	PEAK POWER	USB PORT	AC OUTLETS	REMOTE CONTROL	PACK QTY
10-00482	2000W	4000W	1	3	Yes	2



3000W Power Inverter (cables sold separately)

ITEM PN#	MAX CONTINUOUS POWER	PEAK POWER	USB PORT	AC OUTLETS	REMOTE CONTROL	PACK QTY
10-00483	3000W	6000W	1	3	Yes	1

PRO SERIES product



2000W Pure Sine Power Inverter

ITEM PN#	MAX CONTINUOUS POWER	PEAK POWER	USB PORT	AC OUTLETS	REMOTE CONTROL	PACK QTY
10-00487	2000W	4000W	1	2	Yes	2

- LCD Panel Display
- Overload Protection

Power Inverter Accessories

ITEM PN#	DESCRIPTION	PACK QTY
10-00484	Cable Kit 1000-1500W	1 set-3ft/6g Wire Cable with Ring Terminals
10-00485	Cable Kit 2000-3000W	1 set-3ft/4g Wire Cable with Ring Terminals
10-00486	Remote Control	Remote Control for 1000-3000W Inverters





E-ZEEGRIP handle folds down to fit flush with electrical enclosures.

LIMITED
LIFETIME WARRANTY

COMPARE THE QUALITY

VOLTEC
POWER & LIGHTING

RV Adapters & Extension Cords

PRO SERIES product

15-30 AMP Adapter with **E-ZEEGRIP**

ITEM PN#	CORD LENGTH	WIRE GAUGE	WIRE TYPE	WIRE COLOR	OUTLETS	PLUG TYPE	RECEPTACLE TYPE	POWER RATING AMPS	WATTS	PACK QTY
16-00502	12in	10/3	STW	Blue/Yellow	1	5-15P	30A	15	1875	10



30-15 AMP Adapter with **E-ZEEGRIP**

ITEM PN#	CORD LENGTH	WIRE GAUGE	WIRE TYPE	WIRE COLOR	OUTLETS	PLUG TYPE	RECEPTACLE TYPE	POWER RATING AMPS	WATTS	PACK QTY
16-00503	12in	10/3	STW	Blue/Yellow	1	30A	5-15R	15	1875	10



30-50 AMP Adapter with **E-ZEEGRIP**

ITEM PN#	CORD LENGTH	WIRE GAUGE	WIRE TYPE	WIRE COLOR	OUTLETS	PLUG TYPE	RECEPTACLE TYPE	POWER RATING AMPS	WATTS	PACK QTY
16-00504	18in	10/3	STW	Blue/Yellow	1	30A	50A	15	1875	10



50-30 AMP Adapter with **E-ZEEGRIP**

ITEM PN#	CORD LENGTH	WIRE GAUGE	WIRE TYPE	WIRE COLOR	OUTLETS	PLUG TYPE	RECEPTACLE TYPE	POWER RATING AMPS	WATTS	PACK QTY
16-00505	18in	10/4	STW	Blue/Yellow	1	50A	30A	15	1875	10



30 AMP Locking Adapter with **E-ZEEGRIP**

ITEM PN#	CORD LENGTH	WIRE GAUGE	WIRE TYPE	WIRE COLOR	OUTLETS	PLUG TYPE	RECEPTACLE TYPE	POWER RATING AMPS	WATTS	PACK QTY
16-00506	18in	10/3	STW	Blue/Yellow	1	L5-30P	30A	15	1875	10
16-00526	18in	10/4	STW	Blue/Yellow	1	L14-30P	30A	15	1875	10



30 AMP RV Extension Cord with **E-ZEEGRIP**

ITEM PN#	CORD LENGTH	WIRE GAUGE	WIRE TYPE	WIRE COLOR	OUTLETS	PLUG TYPE	RECEPTACLE TYPE	POWER RATING AMPS	WATTS	PACK QTY
16-00507	10ft	10/3	STW	Blue/Yellow	1	30A	30A	15	1875	4
16-00508	25ft	10/3	STW	Blue/Yellow	1	30A	30A	15	1875	2
16-00509	50ft	10/3	STW	Blue/Yellow	1	30A	30A	15	1875	1



50 AMP RV Extension Cord with **E-ZEEGRIP**

ITEM PN#	CORD LENGTH	WIRE GAUGE	WIRE TYPE	WIRE COLOR	OUTLETS	PLUG TYPE	RECEPTACLE TYPE	POWER RATING AMPS	WATTS	PACK QTY
16-00510	15ft	6/3-8/1	STW	Blue/Yellow	1	50A	50A	15	1875	2
16-00511	30ft	6/3-8/1	STW	Blue/Yellow	1	50A	50A	15	1875	1



E-ZEEGRIP Replacement Handle

16-00548	Yellow Replacement Handle for 30AMP	PACK QTY: 2
16-00549	Yellow Replacement Handle for 50AMP	PACK QTY: 2



RV Locking Extension Cords with **E-ZEE GRIP**

RV Extension Cord with Locking Tight Female Receptacle


ITEM PN#	CORD LENGTH	WIRE GAUGE	WIRE TYPE	WIRE COLOR	OUTLETS	PLUG TYPE	RECEPTACLE TYPE	PACK QTY
16-00584	25ft	10/3	STW	Blue/Yellow	1	30A	30A	2
16-00585	35ft	10/3	STW	Blue/Yellow	1	30A	30A	2
16-00586	25ft	6/3-8/1	STW	Blue/Yellow	1	50A	50A	2
16-00587	35ft	6/3-8/1	STW	Blue/Yellow	1	50A	50A	1
16-00588	25ft	10/3	STW	Blue/Yellow	1	30A	50A	
16-00589	25ft	10/3	STW	Blue/Yellow	1	50A	30A	
16-00590	2ft	10/3	STW	Blue/Yellow	1	30A	30A	
16-00591	2ft	10/3	STW	Blue/Yellow	1	30A	50A	

PRO SERIES product



RV Extension Cord with Locking Tight Female Receptacle

16-00592	2ft	10/3	STW	Blue/Yellow	1	5-15P	30A	
----------	-----	------	-----	-------------	---	-------	-----	--



Adapters

Park Adapters

ITEM PN#	OUTLETS	PLUG TYPE	RECEPTACLE TYPE	PACK QTY
16-00500	1	5-15P	30A	10/100
16-00501	1	30A	5-15R	10/100
16-00550	1	5-15P	30A	10/100
16-00551	1	50A	5-15R	10/100




Park Generator Adapter

16-00516	1	L5-30P	30A	10/50
----------	---	--------	-----	-------

Heavy Duty Molded Adapters

ITEM PN#	OUTLETS	PLUG TYPE	RECEPTACLE TYPE	PACK QTY
16-00582	1	30A	50A	10/50
16-00583	1	50A	30A	10/50




Flat Wire Adapters

ITEM PN#	CORD LENGTH	GAUGE	PLUG TYPE	RECEPTACLE TYPE	PACK QTY
16-00568	12in	10/3	5-15P	30A	10
16-00569	12in	10/3	30A	5-15R	10
16-00570	18in	10/3	30A	50A	10
16-00571	18in	10/3	50A	30A	10



30 AMP Replacement Heads

ITEM PN#	DESCRIPTION	PACK QTY
16-00580	Male 30A Replacement Head	10
16-00581	Female 30A Replacement Head	10



RV Adapter and Extension Cords

Traditional Series

15-30 AMP Adapter

ITEM PN#	CORD LENGTH	WIRE GAUGE	WIRE TYPE	WIRE COLOR	OUTLETS	PLUG TYPE	RECEPTACLE TYPE	POWER RATING AMPS WATTS	PACK QTY
16-00552	12in	10/3	STW	Black	1	5-15P	30A	15 1875	10



30-15 AMP Adapter

ITEM PN#	CORD LENGTH	WIRE GAUGE	WIRE TYPE	WIRE COLOR	OUTLETS	PLUG TYPE	RECEPTACLE TYPE	POWER RATING AMPS WATTS	PACK QTY
16-00553	12in	10/3	STW	Black	1	30A	5-15R	15 1875	10



30-50 AMP Adapter

ITEM PN#	CORD LENGTH	WIRE GAUGE	WIRE TYPE	WIRE COLOR	OUTLETS	PLUG TYPE	RECEPTACLE TYPE	POWER RATING AMPS WATTS	PACK QTY
16-00554	18in	10/3	STW	Black	1	30A	50A	15 1875	10



50-30 AMP Adapter

ITEM PN#	CORD LENGTH	WIRE GAUGE	WIRE TYPE	WIRE COLOR	OUTLETS	PLUG TYPE	RECEPTACLE TYPE	POWER RATING AMPS WATTS	PACK QTY
16-00555	18in	10/4	STW	Black	1	50A	30A	15 1875	10



30 AMP and 50 AMP RV Extension Cord

ITEM PN#	CORD LENGTH	WIRE GAUGE	WIRE TYPE	WIRE COLOR	OUTLETS	PLUG TYPE	RECEPTACLE TYPE	POWER RATING AMPS WATTS	PACK QTY
16-00557	10ft	10/3	STW	Black	1	30A	30A	15 1875	4
16-00558	25ft	10/3	STW	Black	1	30A	30A	15 1875	2
16-00559	50ft	10/3	STW	Black	1	30A	30A	15 1875	1
16-00561	30ft	6/3-8/1	STW	Black	1	50A	50A	15 1875	2



RV Power Supply Cords

30 AMP Right Angle Power Supply Cord

ITEM PN#	CORD LENGTH	WIRE GAUGE	WIRE TYPE	WIRE COLOR	OUTLETS	PLUG TYPE	POWER RATING AMPS WATTS	PACK QTY
16-00562	25ft	10/3	STW	Black	1	30A	15 1875	2
16-00566	30ft	10/3	STW	Black	1	30A	15 1875	2



50 AMP Right Angle Power Supply Cord

ITEM PN#	CORD LENGTH	WIRE GAUGE	WIRE TYPE	WIRE COLOR	OUTLETS	PLUG TYPE	POWER RATING AMPS WATTS	PACK QTY
16-00563	25ft	6/3-8/1	STW	Black	1	50A	15 1875	2
16-00567	36ft	10/3	STW	Black	1	50A	15 1875	2



30 AMP Right Angle Male and Female Pigtail

ITEM PN#	CORD LENGTH	WIRE GAUGE	WIRE TYPE	WIRE COLOR	OUTLETS	PLUG TYPE	POWER RATING AMPS WATTS	PACK QTY
16-00564	18in	10/3	STW	Black	1	30A Male	15 1875	10
16-00565	18in	10/3	STW	Black	1	30A Female	15 1875	10



Outdoor 300V SJTW Convention Center Cords -40°F to 140°F

Voltec's new convention center cords are manufactured to the UL 817 Cord Set Standards and are covered under the UL 2305 Exhibition Display Units and Installation Standards. These cordsets are offered in custom colors and legends.



Multi-Outlet Extension Cord

ITEM PN#	CORD LENGTH	WIRE GAUGE	WIRE TYPE	WIRE COLOR	OUTLETS	PLUG TYPE	RECEPTACLE TYPE	POWER RATING AMPS WATTS	PACK QTY
02-00023	20ft	12/3	SJTW	Yellow	5	5-15P	5-15R	15 1875	12
02-00024	40ft	12/3	SJTW	Yellow	9	5-15P	5-15R	15 1875	6

Optional Accessories for Convention Centers

Power Distribution



page 19

Cord Reels



page 26

Generator
Adapters



page 16

LED Lighting



page 36

Lighting Replacement Parts

Work Light Replacement Parts

ITEM PN#		PACK QTY
08-00288	Plastic Replacement Bulb Guard	12
08-00286	Metal Replacement Bulb Guard	12
08-00287	Industrial Metal Replacement Bulb Guard	12
08-00289	Handle and Switch Assembly for Trouble Lights	6
08-00290	Trouble Light Replacement Head w/ Metal Cage	6



Fluorescent Work Light Replacement Parts

ITEM PN#		PACK QTY
08-00291	Replacement Head for 13W Fluorescent Tube Light	6
08-00292	Replacement Lens for 13W Fluorescent Tube Light	6/60
08-00293	Replacement Lens for 15W Fluorescent Tube Light	6/60
08-00294	Replacement Head for 13W Fluorescent Angle Light	6
08-00295	Replacement Hook for Angle Light	12
08-00296	Replacement Lens for 13W Fluorescent Angle Light	6/60
08-00297	Replacement Lens for 26W Fluorescent Angle Light	6/60
08-00298	Replacement Magnet for 13W Fluorescent Angle Light	6/60
08-00299	Replacement Magnet for 26W Fluorescent Angle Light	6
08-00273	Replacement Head for 26W Fluorescent Angle Light	6



Replacement Bulbs

ITEM PN#		BULB RATING	PACK QTY
08-00029	Rough Service "A" Bulb	75W	12/120
08-00028	Rough Service "A" Bulb	100W	12/120
00393	Rough Service "A" Bulb	150W	30/120
00365	60W Silicone Coated Bulb	60W	30/120
00378	75W Silicone Coated Bulb	75W	30/120
00391	100W Silicone Coated Bulb	100W	30/120
08-00272	12V Rough Service "A" Bulb	60W	12/120
08-00030	Compact Fluorescent Bulb - 65K	13W	20/200
08-00274	Fluorescent Bulb/T8	15W	20/100
08-00801	65W Fluorescent Bulb	65W	10
08-00802	200W Halogen Bulb	200W	10
08-00803	300W Halogen Bulb	300W	10
08-00031	500W Halogen Bulb	500W	20/100
08-01051	250W Halogen Bulb	250W	25/250
2845	400W Metal Halide Bulb	400W	1/6

