



AFD





An industry leader in LED, fluorescent and other light sources, we have maintained our respected position in the lighting industry. Our growth has paralleled the development and advancement of energy-efficient fluorescent and LED lighting.

By fully understanding the needs and expectations of our customers, we will continue advancing the use of sustainable LED lighting solutions with the focus of reducing energy consumption, operating and maintenance costs.

With versatile, energy-efficient lighting solutions for a wide-range of commercial and residential applications, AFX products provide the performance you need in decorative designs that blend with any architectural style.

# lighting your vision.

## KEY

LED



Dimmable Option



American Disability Act



Fluorescent



Wet Location



Title 24



Design Lights Consortium™



Emergency Battery Backup



ENERGY STAR® Qualified



Lamp Included



Lighting For Tomorrow





Pendant

p.11

Sconce

p.47

Vanity

p.107

Fixed Rail

p.129

Ceiling

p.139

Outdoor

p.179

Overbed

p.205

Decorative Linear

p.219

Undercabinet

p.235

Hera

p.246

MP Lighting

p.254

Reference/Index

p.266

## Pendant Glass



Spun p.13



Hermosa p.15



Armitage p.17



Oketo p.18



View p.21



Soho p.21



Enzo p.22



Aria p.24



Essex p.27



Laveer p.29



Geo p.30



Bella p.31

## Pendant Drum



Ambrose p.32



Apex p.34



Willow p.36



Anton p.37



Dayton p.38



Sanibel p.40



Oslo p.41



Rhome p.42



Montclair p.43



Cortez p.45



Bilbao p.46

# Sconce



Casino p.49



Charlotte p.51



Arden p.53



Zoe p.55



Fulton p.57



Post p.59



Novara p.61



Aberdeen p.63



Oketo p.64



Apex p.66



Eden p.67



Sinclair p.68




Noma p.69



Lyon p.70




Geneva p.71



Axel p.72



Maddox p.72



Anton p.73



Ellipse p.74



Kass p.75



Wells p.76



Genesis p.78



Cortez p.80



Tory p.83



Sheridan p.85



Nolan p.87




Bella p.88



Laveer p.89



Montrose p.90



Taylor p.91




Delany p.92



Restoration p.93



Aria p.94



Lancet p.95



Trillium p.96



Brio p.97

## Sconce Continued



Algers p.98



Ideal p.99



Monroe p.100



Rio p.101



Bilbao p.102



Century p.103



Fusion p.104



Lasalle p.105



Unity p.106

## Vanity



Novara p.108



Arden p.109



Sinclair p.110



Charlotte p.111



Cortez p.112



Pacific p.113



Algers p.114



Aria p.116



Century p.117



Taylor p.118



Bilbao p.119



Fusion p.120



Vernon p.121



Rio p.122



Evolution p.124



Nolan p.125



Stratus p.126



Vista p.127



Atwater p.128


## Fixed Rail



District p.131




Gramercy p.133




Chappelle p.134



Metro p.136



Core p.137



Cantrell p.138

## Ceiling



Boon p.141



Reveal p.143



Alta p.145



Sinclair p.146



Sloane p.147



Zurich p.148



Atlas p.149



Sutton p.150



Axel p.151



Maddox p.151



Apex p.152



Cortez p.153



Montclair p.154



Eden p.155



Sanibel p.156



Anton p.157



Willow p.158



Oslo p.159



Nolan p.160



Algiers p.161



Lyon p.162



Geneva p.163




Delany p.164



Monroe p.165



Sheridan p.166



Hudson p.167



Taylor p.168



Restoration p.170



Century p.171



Fusion p.172

## Ceiling Continued



Bilbao p.173



Carlisle p.174



Capri p.175



Ideal p.176



Covina p.177



Camden p.178



Carter p.178



Cirrus p.178

## Outdoor



Blaine p.181



Beaumont p.183



Avenue p.185



Logan p.187



Max p.189



State p.191



Brio p.192



Aria Mini Flush  
p.194



Aria Mini p.195



Aria p.196



Century p.197



Bilbao p.199



Bronson p.200



Hanover p.201



Fusion p.202



LED Security  
p.203



LED Security  
p.203



LED Flood  
p.204



LED Flood  
p.204

## Overbed



Harvard p.206



Randolph p.207



Clayton p.208



Sheffield p.209



Algiers p.210



Sheridan p.211



Ideal p.213



Hinsdale p.214



Cameron p.215



Bilbao p.216



Palmetto p.218

## Decorative Linear



Zurich p.220




Sloan p.221




Atlas p.222



Highland p.223




Aeon Suspended p.224



Aeon p.225




Gizelle p.226



Mission p.226



Winchester p.227



Conroe p.227



LED Cloud p.228



Courtland p.228




## Decorative Linear Continued




Largo p.229



Rigby p.229



Marina p.230



Malibu p.230



LED Wrap p.231




Narrow Wrap p.231



LED Striplight p.232




Striplight p.232



Commercial Striplight p.233



T5 Striplight p.233



LED Vaportight p.234




Vaportight p.234


## Undercabinet




Slate Pro p.238



LED Noble Pro p.240




LED T5L p.242



Xenon NXL p.243



T5 Fluorescent p.244



T8 Fluorescent p.244



# PENDANT



Clear



Smoke



Steel Blue



# SPUN

- Hand-blown glass with white pattern molten glass cane
- White inner glass
- 9 ft. adjustable cord with twist lock strain relief

## LED

- 50,000 hr. LED life, available in 1000 lumens (10W), 90 CRI

5" DIA. x 16-3/4" H

Series	Source Lumens	LED	CCT	Driver	Finish	Glass	Canopy Options
SPP	1000	L	30 3000K	D1 Voltage (120V TRIAC Dimming) D2 Voltage (120-277V 0-10V Dimming)	SN Satin Nickel	CL Clear SM Smoke SB Steel Blue	Blank Monopoint LNR3 (3) Light Linear RND3 (3) Light Round RND6 (6) Light Round

Example: SPP1000L30D2SNSMLNR3



PENDANT



Clear Swirl



Brown



Aqua



Clear

# HERMOSA

- Clear or tinted outer glass
- White inner glass
- 9 ft. adjustable cord with twist lock strain relief

## LED

- 50,000 hr. LED life, available in 1000 lumens (10W), 90 CRI

6" DIA. x 16" H

<b>Series</b> HRP	<b>Source Lumens</b> 1000	<b>LED</b> L	<b>CCT</b> 30 3000K	<b>Driver</b> D1 Voltage (120V TRIAC Dimming) D2 Voltage (120-277V 0-10V Dimming)	<b>Finish</b> SN Satin Nickel	<b>Glass</b> AQ Aqua CL Clear CS Clear Swirl BR Brown	<b>Canopy Options</b> Blank Monopoint LNR3 (3) Light Linear RND3 (3) Light Round RND6 (6) Light Round
----------------------	------------------------------	-----------------	------------------------	---	----------------------------------	---	---

Example: HRP1000L30D1SNAQ



PENDANT



Brown

Clear Crackle



Clear



Aqua

# ARMITAGE

- Clear or tinted outer glass
- White inner glass
- 9 ft. adjustable cable with twist lock strain relief

## LED

- 50,000 hr. LED life, available in 500 lumens (6W), 90 CRI

10" DIA. x 8" H

Series	Source Lumens	LED	CCT	Driver	Finish	Glass
AGP	500	L	30 3000K	D1 Voltage (120V TRIAC Dimming) D2 Voltage (120-277V 0-10V Dimming)	SN Satin Nickel	AQ Aqua CC Clear Crackle CL Clear BR Brown

Example: AGP500L30DISNCL





Black

# OKETO

- Aluminum cylinder with powder coated finish
- 8 ft. adjustable cable

## LED

- 50,000 hr. LED life, available in 700 lumens (7W), 90 CRI



Silver

White

Black/  
Clear Crackle

Series	Size (Inches)		Source Lumens	LED	CCT	Driver
	DIA.	H				
OTP	2	06	700	L	27 2700K	D1 Voltage (120V TRIAC Dimming) D2 Voltage (120-277V 0-10V Dimming)
		12			30 3000K	
		18				

**Color**  
BK Black  
SL Silver  
WH White

**Finish**  
SN Satin Nickel


**Glass Diffuser Options\***  
Blank No Diffuser  
CC Clear Crackle  
CS Clear Seeded

Example: OTP218700L30DIBKSNCC

\*Add 1-1/2" to length of fixture



See page 267 for listing of expanded colors



## Companion







PENDANT

Expanded Color  
Purple





White

# VIEW

- Frosted inner glass
- Clear outer glass
- 9 ft. adjustable cord with twist lock strain relief


## LED

- 50,000 hr. LED life, available in 1000 lumens (10W), 90 CRI

4-5/8" DIA. x 16" H

<b>Series</b> VIP	<b>Source Lumens</b> 1000	<b>LED</b> L	<b>CCT</b> 30 3000K	<b>Driver</b> D1 Voltage (120V TRIAC Dimming) D2 Voltage (120-277V 0-10V Dimming)	<b>Finish</b> SN Satin Nickel	<b>Glass</b> AM Amber CR Cream WH White	<b>Canopy Options</b> Blank Monopoint LNR3 (3) Light Linear RND3 (3) Light Round RND6 (6) Light Round
----------------------	------------------------------	-----------------	------------------------	---	----------------------------------	--	---

Example: VIP1000L30D1SNCRNRND6



Amber

Cream

White

# SOHO

- Frosted glass
- 9 ft. adjustable cord with twist lock strain relief


## LED

- 50,000 hr. LED life, available in 1000 lumens (10W), 90 CRI

3-7/8" DIA. x 14" H

<b>Series</b> SSP	<b>Source Lumens</b> 1000	<b>LED</b> L	<b>CCT</b> 30 3000K	<b>Driver</b> D1 Voltage (120V TRIAC Dimming) D2 Voltage (120-277V 0-10V Dimming)	<b>Finish</b> SN Satin Nickel	<b>Glass</b> AM Amber CR Cream WH White	<b>Canopy Options</b> Blank Monopoint LNR3 (3) Light Linear RND3 (3) Light Round RND6 (6) Light Round
----------------------	------------------------------	-----------------	------------------------	---	----------------------------------	--	---

Example: SSP1000L30D2SNWH



Amber

Cream

White



# ENZO

- Clear or tinted outer glass
- White inner glass
- 9 ft. adjustable cord with twist lock strain relief

## LED


- 50,000 hr. LED life, available in 1000 lumens (10W), 90 CRI

5-3/4" DIA. x 17" H

Series	Source Lumens	LED	CCT	Driver	Finish	Glass	Canopy Options
ENP	1000	L	30 3000K	D1 Voltage (120V TRIAC Dimming) D2 Voltage (120-277V 0-10V Dimming)	SN Satin Nickel	AM Amber CL Clear GR Green RD Red	Blank Monopoint LNR3 (3) Light Linear RND3 (3) Light Round RND6 (6) Light Round

Example: ENP1000L30D2SNCRND3

**LED** **DIM**





Amber



Red



Green

PENDANT

# ARIA

- Frosted white glass diffuser
- 6 ft. adjustable cord with twist lock strain relief

## FLUORESCENT

- 120V electronic socket ballast
- Lamps not included



Satin Nickel	Type	Qty.	Lamp	DIA.	H
ARPI13SNEC	Singular	1	13W CFQ 4-Pin	2-7/8"	10-1/8"
ARPC313SNEC	Circular	3	13W CFQ 4-Pin	-	10-1/8"
ARPB313SNEC	Linear	3	13W CFQ 4-Pin	-	10-1/8"



Companion





PENDANT



Blue



Red

White





Amber

# ESSEX

- Mini glass pendant
- 9 ft. adjustable cable

## LED

- 50,000 hr. LED life, available in 500 lumens (6W), 90 CRI

4-1/4" DIA. x 5" H

Series	Source Lumens	LED	CCT	Driver	Finish	Glass	Canopy Options
SXPL	500	L	30 3000K	D1 Voltage (120V TRIAC Dimming) D2 Voltage (120-277V 0-10V Dimming)	SN Satin Nickel	AM Amber BU Blue RD Red WH White	Blank Monopoint LNR3 (3) Light Linear RND3 (3) Light Round RND6 (6) Light Round

Example: SXPL500L30D2SNWH





Green



Blue

# LAVEER

- Mini glass pendant
- 9 ft. adjustable cable

## LED

- 50,000 hr. LED life, available in 500 lumens (6W), 90 CRI

4-1/2" DIA. x 7" H

Series	Source Lumens	LED	CCT	Driver
LAPL	500	L	30 3000K	D1 Voltage (120V TRIAC Dimming) D2 Voltage (120-277V 0-10V Dimming)




White

Amber

Finish	Glass	Canopy Options
SN Satin Nickel	AM Amber BU Blue GR Green WH White	Blank Monopoint LNR3 (3) Light Linear RND3 (3) Light Round RND6 (6) Light Round

Example: LAPL500L30D2SNGRRND6



Companion



PENDANT



# GEO

- Mini glass pendant
- 9 ft. adjustable cable


## LED

- 50,000 hr. LED life, available in 500 lumens (6W), 90 CRI

3-1/8" DIA. x 3-7/8" H

Series	Source Lumens	LED	CCT	Driver	Finish	Glass	Canopy Options
GEPL	500	L	30 3000K	D1 Voltage (120V TRIAC Dimming) D2 Voltage (120-277V 0-10V Dimming)	SN Satin Nickel	WH White	Blank Monopoint LNR3 (3) Light Linear RND3 (3) Light Round RND6 (6) Light Round

Example: SXPL500L30D2SNWH



Red




# BELLA

- Mini glass pendant
- 9 ft. adjustable cable

## LED

- 50,000 hr. LED life, available in 500 lumens (6W), 90 CRI



Amber

Blue

White


3-3/8" DIA. x 6-1/2" H

Series	Source Lumens	LED	CCT	Driver	Finish	Glass	Canopy Options
BEPL	500	L	30 3000K	D1 Voltage (120V TRIAC Dimming) D2 Voltage (120-277V 0-10V Dimming)	SN Satin Nickel	AM Amber BU Blue RD Red WH White	Blank Monopoint LNR3 (3) Light Linear RND3 (3) Light Round RND6 (6) Light Round

Example: BEPL500L30D1SNRD



Companion





Jute

# AMBROSE

- LumaFuse™ laminated fabric/acrylic shade
- Concave white bottom acrylic diffuser
- Adjustable aircraft cable provided
- 8 ft. adjustable cord/cable for 120V applications
- 3 ft. adjustable rigid stem for 120-277V applications

## LED


- 50,000 hr. LED life, available in 1400 lumens (15W) or 2400 lumens (24W), 90 CRI

19" DIA. x 5" H

24" DIA. x 8" H

Series	Size (Inches)		Source Lumens	LED	CCT	Driver	Finish	Shade
	DIA.	H						
ABP	19	5	1400	L	27 2700K	D1 Voltage (120V TRIAC Dimming) D2 Voltage (120-277V 0-10V Dimming)	SN Satin Nickel	JT Jute LW Linen White
	24	8	2400		30 3000K			

Example: ABP242400L30D2SN-LW



Jute



Linen White



Linen White

PENDANT



Espresso/Jute

# APEX

- Solid wood accent detail
- LumaFuse™ laminated fabric/acrylic shade
- White bottom acrylic diffuser
- Adjustable aircraft cable provided
- 8 ft. adjustable cord/cable for 120V applications
- 3 ft. adjustable rigid stem for 120-277V applications

## LED

- 50,000 hr. LED life, available in 1400 lumens (15W), 2400 lumens (24W) or 3200 lumens (35W), 90 CRI

12-1/4" DIA. x 3-1/2" D	<b>With Wood Accent</b>
15" DIA. x 3-1/2" D	14-1/4" DIA. x 4-1/4" D
19-1/4" DIA. x 3-1/2" D	17" DIA. x 4-1/4" D
	21-1/4" DIA. x 4-1/4" D

Series	Size (Inches)	Source Lumens	LED	CCT	Driver	Wood Finish	Shade
APP	12	= 1400	L	27 2700K	D1 Voltage (120V TRIAC Dimming)	ES Espresso	JT Jute
	15	= 2400		30 3000K	D2 Voltage (120-277V 0-10V Dimming)	WG Weathered Grey	LW Linen White
	19	= 3200					

Example: APP152400L30D2ES-LW

Companion





Weathered Grey/Linen White

PENDANT



# WILLOW

- LumaFuse™ laminated veneer/acrylic shade
- White bottom acrylic diffuser
- Adjustable aircraft cable provided
- 8 ft. adjustable cord/cable for 120V applications
- 3 ft. adjustable rigid stem for 120-277V applications

## LED

- 50,000 hr. LED life, available in 1400 lumens (15W), 2400 lumens (25W) or 3200 lumens (35W), 90 CRI

12-1/4" DIA. x 4-7/8" H

15" DIA. x 4-7/8" H

19-1/4" DIA. x 4-7/8" H

Series	Size (Inches)		LED	CCT	Driver	Finish	Color
	DIA.	Source Lumens					
WLP	12	= 1400	L	27 2700K	D1 Voltage (120V TRIAC Dimming) D2 Voltage (120-277V 0-10V Dimming)	SN Satin Nickel	GV Grey Veneer
	15	= 2400		30 3000K			
	19	= 3200					

Example: WLP152400L30D2SN-GV



Companion





Jute

# ANTON

- LumaFuse™ laminated fabric/acrylic shade
- White bottom acrylic diffuser
- Adjustable aircraft cable provided
- 8 ft. adjustable cord for 120V applications
- 3 ft. adjustable rigid stem for 120-277V applications

## LED

- 50,000 hr. LED life, available in 1400 lumens (15W), 2400 lumens (25W) or 3200 lumens (35W), 90 CRI

12-1/4" DIA. x 4-3/4" H

15" DIA. x 5-1/2" H

19-1/4" DIA. x 5-1/2" H

Series	Size (Inches)		LED	CCT	Driver	Finish	Shade
	DIA.	Source Lumens					
ANP	12	= 1400	L	27 2700K	D1 Voltage (120V TRIAC Dimming) D2 Voltage (120-277V 0-10V Dimming)	SN Satin Nickel	JT Jute LW Linen White
	15	= 2400		30 3000K			
	19	= 3200					

Example: ANP121400L30D2SN-LW



Jute



Linen White

### Companion



Linen White



# DAYTON

- Two-tier white linen fabric shade
- White bottom acrylic diffuser
- Adjustable aircraft cable provided
- 8 ft. adjustable cord/cable for 120V applications
- 3 ft. adjustable rigid stem for 120-277V applications

## LED

- 120V TRIAC dimmable (D1)
- 120-277V universal-voltage driver, 0-10V dimming (D2)
- 50,000 hr. LED life, 90 CRI

Satin Nickel	LED	Source Lumens	CCT	DIA.	H
DYP243200L27D1SN	35W	3200	2700K	24"	9"
DYP243200L27D2SN	35W	3200	2700K	24"	9"
DYP243200L30D1SN	35W	3200	3000K	24"	9"
DYP243200L30D2SN	35W	3200	3000K	24"	9"
DYP304400L27D1SN	40W	4400	2700K	30"	12"
DYP304400L27D2SN	40W	4400	2700K	30"	12"
DYP304400L30D1SN	40W	4400	3000K	30"	12"
DYP304400L30D2SN	40W	4400	3000K	30"	12"


## FLUORESCENT

- 120-277V universal-voltage ballast
- 8 ft. adjustable cord/cable
- Lamps not included

Satin Nickel	Qty.	Lamp	DIA.	H
DYP418SNMV	4	18W CFQ 4-Pin	24"	9"
DYP618SNMV	6	18W CFQ 4-Pin	30"	12"



**LED DIM**





PENDANT



Linen White

# SANIBEL

- LumaFuse™ laminated fabric/acrylic outer diffuser
- White acrylic inner diffuser
- Adjustable aircraft cable provided
- 8 ft. adjustable cord/cable for 120V applications
- 3 ft. adjustable rigid stem for 120-277V applications

## LED

- 50,000 hr. LED life, available in 1400 lumens (15W), 2400 lumens (25W) or 3200 lumens (35W), 90 CRI


16" DIA. x 5-5/8" H  
 18" DIA. x 5-5/8" H  
 23-1/4" DIA. x 5-5/8" H



Jute

Series	Size (Inches)		LED	CCT	Driver	Finish	Shade
	DIA.	Source Lumens					
SAP	16	= 1400	L	27	2700K 30 3000K	D1 Voltage (120V TRIAC Dimming) D2 Voltage (120-277V 0-10V Dimming)	SN Satin Nickel
	18	= 2400					
	23	= 3200					

Example: SAPI82400L30DISN-JT



## Companion





Jute

# OSLO

- LumaFuse™ laminated fabric/acrylic shade
- White domed bottom acrylic diffuser
- Adjustable aircraft cable provided
- 8 ft. adjustable cord/cable for 120V applications
- 3 ft. adjustable rigid stem for 120-277V applications

## LED

- 50,000 hr. LED life, available in 1400 lumens (15W), or 2400 lumens (35W), 90 CRI


17" DIA. x 4-1/2" H  
24" DIA. x 5-3/4" H



Linen White

Series	Size (Inches)		LED	CCT	Driver	Finish	Shade
	DIA.	Source Lumens					
OSP	17	= 1400	L	27 2700K	D1 Voltage (120V TRIAC Dimming) D2 Voltage (120-277V 0-10V Dimming)	SN Satin Nickel	JT Jute LW Linen White
	24	= 2400		30 3000K			

Example: OSP171400L27D2SN-LW



Jute



Linen White

Companion







Linen White

# RHOME

- LumaFuse™ laminated fabric/acrylic two-tier shade
- White bottom acrylic diffuser
- Adjustable aircraft cable provided
- 8 ft. adjustable cord/cable for 120V applications
- 3 ft. adjustable rigid stem for 120-277V applications

## LED

- 50,000 hr. LED life, available in 3200 lumens (35W) or 4400 lumens (40W), 90 CRI

24" DIA. x 9-3/4" H


30" DIA. x 9-1/2" H



Jute

Series	Size (Inches)		LED	CCT	Driver	Finish	Shade
	DIA.	Source Lumens					
RHP	24	= 3200	L	27 2700K 30 3000K	D1 Voltage (120V TRIAC Dimming) D2 Voltage (120-277V 0-10V Dimming)	SN Satin Nickel	JT Jute LW Linen White
	30	= 4400					

Example: RHP304400L30D2SN-JT



## Companion







# MONTCLAIR

- LumaFuse™ laminated fabric/acrylic shade
- Stepped white acrylic bottom diffuser
- Adjustable aircraft cable provided
- 8 ft. adjustable cord/cable for 120V applications
- 3 ft. adjustable rigid stem for 120-277V applications

## LED

- 50,000 hr. LED life, available in 1400 lumens (15W), 2400 lumens (25W) or 3200 lumens (35W), 90 CRI

12-1/4" DIA. x 3-3/4" H

15" DIA. x 4-3/4" H

19-1/4" DIA. x 5-1/2" H

Series	Size (Inches)		Source Lumens	LED	CCT	Driver	Finish	Shade
	DIA.	L						
MCP	12	=	1400	L	27 2700K 30 3000K	D1 Voltage (120V TRIAC Dimming) D2 Voltage (120-277V 0-10V Dimming)	SN Satin Nickel	BK Black
	15	=	2400					
	19	=	3200					

Example: MCP193200L27D1SN-BK



Companion







White/White

# CORTEZ

- Sheer organza fabric outer shade
- White linen inner shade
- White acrylic bottom diffuser
- Adjustable aircraft cable provided
- 8 ft. adjustable cord/cable for 120V applications
- 3 ft. adjustable rigid stem for 120-277V applications

## LED

- 50,000 hr. LED life, available in 3200 lumens (35W) or 4400 lumens (40W), 90 CRI

24" DIA. x 5" H

30" DIA. x 6" H

Series	Size (Inches)		LED	CCT	Driver	Finish	Shade-In-Shade
	DIA.	Source Lumens					
CZP	24	= 3200	L	30 3000K	D1 Voltage (120V TRIAC Dimming) D2 Voltage (120-277V 0-10V Dimming)	KB Oakley Bronze SN Satin Nickel	WHWH White/White BZWH Bronze/White
	30	= 4400					


Example: CZP243200L30D2KB-BZWH



Bronze/White

PENDANT

**LED** **DIM**



Companion



**AFX**




# BILBAO

- Linear aluminum accent bands
- White acrylic diffuser
- 3 ft. adjustable rigid stem for 120-277V applications

## LED

- 120V TRIAC dimmable (D1)
- 120-277V universal-voltage driver, 0-10V dimming (D2)
- 50,000 hr. LED life, 90 CRI

Satin Aluminum	LED	Source Lumens	CCT	DIA.	H
BBP243200L27D1SA	35W	3200	2700K	24"	24"
BBP243200L27D2SA	35W	3200	2700K	24"	24"
BBP243200L30D1SA	35W	3200	3000K	24"	24"
BBP243200L30D2SA	35W	3200	3000K	24"	24"
BBP364400L27D1SA	40W	4400	2700K	36"	24"
BBP364400L27D2SA	40W	4400	2700K	36"	24"
BBP364400L30D1SA	40W	4400	3000K	36"	24"
BBP364400L30D2SA	40W	4400	3000K	36"	24"



Companion



SCONCE



Satin Nickel



# CASINO


- Modern angular design metal housing
- Painted finish

## LED

- 120V TRIAC dimmable (D1)
- 120-277V universal non-dimmable (MV)
- 50,000 hr. LED life, 90 CRI

White	Satin Nickel	LED	Source Lumens	CCT	H	W	D
COS6101300L30MVWH	COS6101300L30MVSN	18W	1300	3000K	6-1/2"	10"	3-1/4"
COS6101300L30D1WH	COS6101300L30D1SN	18W	1300	3000K	6-1/2"	10"	3-1/4"

**LED** **DIM** **ADA**



SCIONCE



Satin Nickel





Oil-Rubbed Bronze


# CHARLOTTE

- Perforated metal ends
- White linen shade

## LED

- 120-277V universal-voltage driver
- Compatible with residential (TRIAC/ELV) and commercial (0-10V) dimmers
- TRIAC and ELV dimming only at 120V
- 50,000 hr. LED life, 90 CRI

		LED	Source Lumens	CCT	H	W	D
<b>Satin Nickel</b>	<b>Oil-Rubbed Bronze</b>						
CHS614700L27UDSN	CHS614700L27UDRB	7W	700	2700K	13-3/4	5-1/2"	3-3/8"
CHS614700L30UDSN	CHS614700L30UDRB	7W	700	3000K	13-3/4	5-1/2"	3-3/8"



Companion





Satin Nickel



Oil-Rubbed Bronze


# ARDEN

- Walnut finish
- Clear outer glass cylinder
- White inner glass cylinder

## LED

- 120V TRIAC dimmable
- 50,000 hr. LED life, 90 CRI

Satin Nickel	Oil-Rubbed Bronze	LED	Source Lumens	CCT	H	W	D
RNS5161200L30D1SN	RNS5161200L30D1RB	15.5W	1200	3000K	15-3/4"	4-3/4"	4"




Companion





White




# ZOE

- Cube design metal housing
- Indirect light with wall wash effect
- Painted finish

## LED

- 120V TRIAC dimmable (D1)
- 120-277V universal non-dimmable (MV)
- 50,000 hr. LED life, 90 CRI

White	Black	LED	Source Lumens	CCT	H	W	D
ZOS505600L30MVWH	ZOS505600L30MVBK	9W	600	3000K	5"	5"	4"
ZOS505600L30D1WH	ZOS505600L30D1BK	9W	600	3000K	5"	5"	4"





Black




# FULTON

- Fabricated metal housing
- White diffuser
- Powder coated finish
- Vertical or horizontal mounting

## LED

- 120V TRIAC dimmable
- 50,000 hr. LED life, 90 CRI

White		Black		LED	Source Lumens	CCT	H	W	D
FTS4141200L30D1WH		FTS4141200L30D1BK		15.5W	1200	3000K	13-1/2"	4"	3-1/2"
FTS4241800L30D1WH		FTS4241800L30D1BK		23W	1800	3000K	24"	4"	3-1/2"





White





# POST

- Combination metal and painted finish
- Indirect illumination
- Requires a rectangular 2 in. x 4 in. electrical box for installation
- Vertical or horizontal mount

## LED

- 120V TRIAC dimmable
- 50,000 hr. LED life, 90 CRI

Dark Grey	White	LED	Source Lumens	CCT	H	W	D
PTS3151200L30D1SNGY	PTS3151200L30D1SNWH	15.5W	1200	3000K	13-1/2"	4"	3-1/2"








# NOVARA

- Metal housing
- White acrylic diffuser
- Vertical or horizontal mounting

## LED

- 120V TRIAC dimmable
- 50,000 hr. LED life, 90 CRI

Satin Nickel	Source			H	W	D
	LED	Lumens	CCT			
NVS5131200L30D1SN	15.5W	1200	3000K	13"	4-1/2"	3-5/8"
NVV5252400L30D1SN	31W	2400	3000K	25"	4-1/2"	3-5/8"





Espresso/Jute



Weathered Grey/  
Linen White

# ABERDEEN

- LumaFuse™ laminated fabric/acrylic shade
- Solid maple wood backplate and trim

## LED



- 120-277V universal-voltage driver
- Compatible with residential (TRIAC/ELV) and commercial (0-10V) dimmers
- TRIAC and ELV dimming only at 120V
- 50,000 hr. LED life, available in 1400 lumens (15W), 90 CRI

19" H x 5-1/2" W x 3" D

Series	Size (Inches)		Source Lumens	LED	CCT	Driver	Wood Finish	Shade
	W	H						
ADS	5	19	1400	L	27 2700K 30 3000K	UD Voltage (120-277V Universal Dimming)	ES Espresso WG Weathered Grey	JT Jute LW Linen White


Example: ADS5191400L27UDWG-JT

**LED** **DIM** **ADA**





OTS  
Black  
Clear Crackle



# OKETO

- Aluminum cylinder with powder coated finish

## LED

- 50,000 hr. LED life, available in 700 lumens (7W) or 1400 lumens (15W), 90 CRI

10" H x 5" W x 3-3/4" D  
16" H x 5" W x 3-3/4" D  
22" H x 5" W x 3-3/4" D

Series	Size (Inches)		Lumens	LED	CCT	Driver	Color	Finish	Glass Diffuser Option*
	W	H							
OTS	5	10	700	L	27 2700K	D1 Voltage (120V TRIAC Dimming)	BK Black SL Silver WH White	SN Satin Nickel	Blank No Diffuser (No Optic) CC Clear Crackle (No Optic) CS Clear Seeded (No Optic) FL No Diffuser (Flood Optic)
		16			30 3000K				
		22							


15" H x 5" W x 3-3/4" D  
27" H x 5" W x 3-3/4" D

Series	Size (Inches)		Lumens	LED	CCT	Driver	Color	Finish	Glass Diffuser Option*
	W	H							
OTSD	5	15	1400	L	27 2700K	D1 Voltage (120V TRIAC Dimming)	BK Black SL Silver WH White	SN Satin Nickel	Blank No Diffuser (No Optic) CC Clear Crackle (No Optic) CS Clear Seeded (No Optic) FL No Diffuser (Flood Optic)
		27			30 3000K				

Example: OTS5271400L30D1BKSNCC

\*Add 1-1/2" to length of fixture

\*Add 1-1/2" to length of fixture



See page 267 for listing of expanded colors



## Companion





OTSD  
Silver



Espresso/Jute

# APEX

- Solid wood accent detail
- LumaFuse™ laminated fabric/acrylic shade
- White acrylic closed top and bottom

## LED

- 120-277V universal-voltage driver
- Compatible with residential (TRIAC/ELV) and commercial (0-10V) dimmers
- TRIAC and ELV dimming only at 120V
- 50,000 hr. LED life, available in 1400 lumens (15W), 90 CRI




Weathered Grey/  
Linen White

13-1/2" H x 5" W x 3" D

Series	Size (Inches)		Source Lumens	LED	CCT	Driver	Wood Finish	Shade
	W	H						
APS	5	13	1400	L	27 2700K 30 3000K	UD Voltage (120-277V Universal Dimming)	ES Espresso WG Weathered Grey	JT Jute LW Linen White

Example: APS5131400L30UDES-LW



## Companion







Chocolate Oak/Jute

# EDEN

- LumaFuse™ laminated fabric/acrylic shade
- Wood veneer trim detail
- White acrylic closed top and bottom

## LED

- 120-277V universal-voltage driver
- Compatible with residential (TRIAC/ELV) and commercial (0-10V) dimmers
- TRIAC and ELV dimming only at 120V
- 50,000 hr. LED life, available in 1400 lumens (15W), 90 CRI



11-1/4" H x 6" W x 3" D

Series	Size (Inches)		Source Lumens	LED	CCT	Driver	Wood Finish	Shade
	W	H						
EDS	6	11	1400	L	27 2700K 30 3000K	UD Voltage (120-277V Universal Dimming)	CV Chocolate Oak Veneer GV Grey Veneer	JT Jute LW Linen White

Example: EDS6111400L27UDCV-JT



Grey/Linen White





# SINCLAIR

- Metal housing
- Frosted white acrylic diffuser
- Closed top and bottom
- Requires a rectangular 2 in. x 4 in. electrical box for installation


## LED

- 120-277V universal-voltage driver
- Compatible with residential (TRIAC/ELV) and commercial (0-10V) dimmers
- TRIAC and ELV dimming only at 120V
- 50,000 hr. LED life, 90 CRI




Satin Nickel

			Source Lumens	CCT	H	W	D
<b>Satin Nickel</b>	<b>Polished Chrome</b>	<b>LED</b>					
SNS410700L27UDSN	SNS410700L27UDPC	7W	700	2700K	10"	3-3/4"	3"
SNS410700L30UDSN	SNS410700L30UDPC	7W	700	3000K	10"	3-3/4"	3"
SNS4181400L27UDSN	SNS4181400L27UDPC	15W	1400	2700K	18"	3-3/4"	3"
SNS4181400L30UDSN	SNS4181400L30UDPC	15W	1400	3000K	18"	3-3/4"	3"



## Companion





Stainless Steel  
Slotted

# NOMA

- Powder coat with diagonal, slotted or solid face
- White acrylic top and bottom diffuser
- Custom laser cut designs available (consult factory)

## LED

- 50,000 hr. LED life, available in 500 lumens (6W), 80 CRI

4-3/4" H x 5-7/8" W x 3-5/8" D

Series	Size (Inches)		Source Lumens	LED	CCT	Driver	Finish	Die Cut
	W	H						
NMS	6	5	500	L	30 3000K	D1 Voltage (120V TRIAC Dimming) MV Voltage (120V-277V Universal Non-Dimming)	BK Black SS Stainless WH White	DC Diagonal SL Slotted Blank Solid


Example: NMS65500L30MVSS-SL



White  
Solid



Black  
Diagonal



See page 267 for listing of expanded colors



Black Silver White



# LYON

- Powder coated matte white metal housing
- Illuminated outer white frosted acrylic diffuser
- Ceiling or wall mount

## LED

- 120V TRIAC dimmable
- 50,000 hr. LED life, 90 CRI

White	LED	Source Lumens	CCT	DIA.	D
LYF10800L30D1WH	10W	800	3000K	10"	2"
LYF161900L30D1WH	17W	1900	3000K	16"	2"





# GENEVA


- Powder coated matte white metal housing
- Illuminated outer white frosted acrylic diffuser
- Ceiling or wall mount

## LED

- 120V TRIAC dimmable
- 50,000 hr. LED life, 90 CRI

White	LED	Source Lumens	CCT	H	W	D
GAF101300L30D1WH	12W	1300	3000K	10"	10"	2"
GAF162300L30D1WH	17W	2300	3000K	16"	16"	2"

**LED** **DIM** **ADA**





# AXEL

- Powder coated matte white metal housing
- Illuminated white frosted acrylic diffuser
- Ceiling or wall mount

## LED

- 120V TRIAC dimmable
- 50,000 hr. LED life, 90 CRI

White	LED	Source Lumens	CCT	DIA.	D
AXF06800L30D1WH	10W	800	3000K	6"	2"

**LED** **DIM** **ADA**



# MADDOX

- Powder coated matte white metal housing
- Illuminated white frosted acrylic diffuser
- Ceiling or wall mount

## LED

- 120V TRIAC dimmable
- 50,000 hr. LED life, 90 CRI

White	LED	Source Lumens	CCT	H	W	D
MAF606800L30D1WH	10W	800	3000K	6"	6"	2"

**LED** **DIM** **ADA**





Jute

# ANTON

- LumaFuse™ laminated fabric/acrylic shade
- White top and bottom acrylic diffuser


## LED

- 120-277V universal-voltage driver
- Compatible with residential (TRIAC/ELV) and commercial (0-10V) dimmers
- TRIAC and ELV dimming only at 120V
- 50,000 hr. LED life, 90 CRI



Linen White

		LED	Source Lumens	CCT	H	W	D
<b>Linen White</b>	<b>Jute</b>						
ANS108700L27UD-LW	ANS108700L27UD-JT	7W	700	2700K	9-3/4"	9-1/2"	3-7/8"
ANS108700L30UD-LW	ANS108700L30UD-JT	7W	700	3000K	9-3/4"	9-1/2"	3-7/8"
ANS1081400L27UD-LW	ANS1081400L27UD-JT	15W	1400	2700K	9-3/4"	9-1/2"	3-7/8"
ANS1081400L30UD-LW	ANS1081400L30UD-JT	15W	1400	3000K	9-3/4"	9-1/2"	3-7/8"



Jute

Linen White

## Companion





# ELLIPSE


- Powder coated matte white metal housing
- Inner white frosted acrylic diffuser
- Requires a rectangular 2 in. x 4 in. electrical box for installation

## LED

---

- 120V TRIAC dimmable
- 50,000 hr. LED life, 90 CRI

White	LED	Source Lumens	CCT	H	W	D
ELS11081200L30D1WH	18W	1200	3000K	11-1/4"	8.5"	2"







# KASS

- Powder coated matte white metal housing
- Enclosed white frosted acrylic diffuser

## LED

- 120V TRIAC dimmable
- 50,000 hr. LED life, 90 CRI

White	LED	Source Lumens	CCT	H	W	D
KAS508700L30D1WH	12W	700	3000K	8-1/8"	4-3/4"	1-7/8"

**LED** **DIM** **ADA**



# WELLS

- Solid maple construction
- White acrylic diffuser


## LED

- 120-277V universal-voltage driver
- Compatible with residential (TRIAC/ELV) and commercial (0-10V) dimmers
- TRIAC and ELV dimming only at 120V
- 50,000 hr. LED life, available in 1400 lumens (15W) or 2100 lumens (23W), 90 CRI

15-3/4"H x 9-3/4" W x 4" D

Series	Size (Inches)		Source Lumens	LED	CCT	Driver	Wood Finish	Frame
	W	H						
WES	9	15	1400 2100	L	27 2700K 30 3000K	UD Voltage (120-277V Universal Dimming)	ES Espresso WG Weathered Grey	4B Four Bars 6B Six Bars

Example: WES9151400L3027UDWG6B



Weathered Grey

# WELLS MINI

- Solid maple construction
- White acrylic diffuser


## LED

- 120-277V universal-voltage driver
- Compatible with residential (TRIAC/ELV) and commercial (0-10V) dimmers
- TRIAC and ELV dimming only at 120V
- 50,000 hr. LED life, available in 1400 lumens (15W), 90 CRI

12"H x 7" W x 3-3/4" D

Series	Size (Inches)		Source Lumens	LED	CCT	Driver	Wood Finish	Frame
	W	H						
WES	7	12	1400	L	27 2700K 30 3000K	UD Voltage (120-277V Universal Dimming)	ES Espresso WG Weathered Grey	4B Four Bars 6B Six Bars

Example: WES7121400L30UDWG6B



Weathered Grey



Espresso

SCONCE



# GENESIS

- Decorative paper inlay or LumaFuse™ acrylic inlay
- Metal trim accent band

## LED


- 120-277V universal-voltage driver
- Compatible with residential (TRIAC/ELV) and commercial (0-10V) dimmers
- TRIAC and ELV dimming only at 120V
- 50,000 hr. LED life, available in 1400 lumens (15W), 90 CRI

11-1/4" H x 10" W x 4" D

Series	Size (Inches)		Source Lumens	LED	CCT	Driver
	W	H				
GNS	10	11	1400	L	27 2700K 30 3000K	UD Voltage (120-277V Universal Dimming)

Example: GNS10111400L30UDSNSB

**LED** **DIM** **ADA**



## Paper Inlay



Spiral Beige  
Architectural Bronze

Whimzy White  
Satin Nickel

## LumaFuse™ Inlay



Jute  
Architectural Bronze

Linen White  
Satin Nickel

**Finish**  
AB Architectural Bronze  
SN Satin Nickel


**Paper Inlay**  
SB Spiral Beige  
WW Whimzy White

**LumaFuse™ Inlay**  
JT Jute  
LW Linen White



Satin Nickel/Jute

SCONCE



# CORTEZ

- Die-cast metal decorative accents
- Sheer organza fabric outer shade
- White linen inner shade with die-cast details

## LED

- 120-277V universal-voltage driver
- Compatible with residential (TRIAC/ELV) and commercial (0-10V) dimmers
- TRIAC and ELV dimming only at 120V
- 50,000 hr. LED life, 90 CRI



25" H x 6" W x 4" D  
 31-1/4" H x 6" W x 4" D



Satin Nickel  
White/White

Series	Size (Inches)		Source Lumens	LED	CCT	Driver	Finish	Shade-In-Shade
	W	H						
CZS	6	22	= 1400	L	27 2700K 30 3000K	UD Voltage (120-277V Universal Dimming)	KB Oakley Bronze SN Satin Nickel	- WHWH White/White BZWH Bronze/White
	6	31	= 2100					

Example: CZS6221400L27UDKB-BZWH



## Companion





Oakley Bronze  
Bronze/White

SCIONCE



Satin Nickel/  
White Linen



# TORY

- Die-cast metal arms
- White linen (WH) or linen acrylic (LA) shade
- White acrylic top and bottom diffuser

## LED

- 120-277V universal-voltage driver
- Compatible with residential (TRIAC/ELV) and commercial (0-10V) dimmers
- TRIAC and ELV dimming only at 120V
- 50,000 hr. LED life, 90 CRI

### Single Arm

Satin Nickel		Oakley Bronze	LED	Source Lumens	CCT	H	W	D
TYS623700L27UDSNWH	TYS623700L27UDKBNWH	TYS623700L27UDKBWH	7W	700	2700K	22-3/4"	5-5/8"	4"
TYS623700L30UDSNWH	TYS623700L30UDKBNWH	TYS623700L30UDKBWH	7W	700	3000K	22-3/4"	5-5/8"	4"
TYS623700L27UDSNLA	TYS623700L27UDKBLA	TYS623700L27UDKBLA	7W	700	2700K	22-3/4"	5-5/8"	4"
TYS623700L30UDSNLA	TYS623700L30UDKBLA	TYS623700L30UDKBLA	7W	700	3000K	22-3/4"	5-5/8"	4"

### Double Arm

Satin Nickel		Oakley Bronze	LED	Source Lumens	CCT	H	W	D
TYS11231400L27UDSNWH	TYS11231400L27UDKBNWH	TYS11231400L27UDKBWH	15W	1400	2700K	22-3/4"	11-3/8"	4"
TYS11231400L30UDSNWH	TYS11231400L30UDKBNWH	TYS11231400L30UDKBWH	15W	1400	3000K	22-3/4"	11-3/8"	4"
TYS11231400L27UDSNLA	TYS11231400L27UDKBLA	TYS11231400L27UDKBKLA	15W	1400	2700K	22-3/4"	11-3/8"	4"
TYS11231400L30UDSNLA	TYS11231400L30UDKBLA	TYS11231400L30UDKBKLA	15W	1400	3000K	22-3/4"	11-3/8"	4"




Oakley Bronze/  
Linen Acrylic

## FLUORESCENT

- 120-277V universal-voltage ballast
- Only available in 2-light/double arm model
- Lamps not included

Satin Nickel		Oakley Bronze	Qty.	Lamp	H	W	D
TYS1123213QMVSNWH	TYS1123213QMVKBWH	TYS1123213QMVKBWH	2	13W CFQ 4-Pin	22-3/4"	11-3/8"	4"
TYS1123218QMVSNWH	TYS1123218QMVKBWH	TYS1123218QMVKBWH	2	18W CFQ 4-Pin	22-3/4"	11-3/8"	4"
TYS1123226QMVSNWH	TYS1123226QMVKBWH	TYS1123226QMVKBWH	2	26W CFQ 4-Pin	22-3/4"	11-3/8"	4"
TYS1123213QMVSNLA	TYS1123213QMVKBKLA	TYS1123213QMVKBKLA	2	13W CFQ 4-Pin	22-3/4"	11-3/8"	4"
TYS1123218QMVSNLA	TYS1123218QMVKBKLA	TYS1123218QMVKBKLA	2	18W CFQ 4-Pin	22-3/4"	11-3/8"	4"
TYS1123226QMVSNLA	TYS1123226QMVKBKLA	TYS1123226QMVKBKLA	2	26W CFQ 4-Pin	22-3/4"	11-3/8"	4"





Satin Nickel/  
Linen Acrylic

# SHERIDAN

- Single or double die-cast metal arm
- Linen acrylic (LA) shade with satin nickel finish or cream linen (LN) shade with champagne finish

## LED

- 120-277V universal-voltage driver
- Compatible with residential (TRIAC/ELV) and commercial (0-10V) dimmers
- TRIAC and ELV dimming only at 120V
- 50,000 hr. LED life, 90 CRI

### Single Arm

Satin Nickel	Champagne	LED	Source Lumens	CCT	H	W	D
SHS618700L27UDSNLA	SHS618700L27UDACLN	7W	700	2700K	18-1/2"	6-1/8"	4"
SHS618700L30UDSNLA	SHS618700L30UDACLN	7W	700	3000K	18-1/2"	6-1/8"	4"

### Double Arm

SHS12181400L27UDSNLA	SHS12181400L27UDACLN	15W	1400	2700K	18"	12-5/8"	4"
SHS12181400L30UDSNLA	SHS12181400L30UDACLN	15W	1400	3000K	18"	12-5/8"	4"



## FLUORESCENT


- 120-277V universal-voltage ballast
- Lamp(s) not included

### Single Arm

Satin Nickel	Champagne	Qty.	Lamp	H	W	D
SHS0618113QMVSNLA	-	1	13W CFQ 4-Pin	18-1/2"	6-1/8"	4"
-	SHS0618118QMVAACLN	1	18W CFQ 4-Pin	18-1/2"	6-1/8"	4"

### Double Arm

SHS1218213QMVSNLA	-	2	13W CFQ 4-Pin	18"	12-5/8"	4"
-	SHS1218218QMVAACLN	2	18W CFQ 4-Pin	18"	12-5/8"	4"



### Companion



Champagne/  
Cream Linen

Oakley Bronze





# NOLAN

- Die-cast metal housing with accents
- Clear outer glass
- White acrylic inner diffuser

## LED


- 120-277V universal-voltage driver
- Compatible with residential (TRIAC/ELV) and commercial (0-10V) dimmers
- TRIAC and ELV dimming only at 120V
- 50,000 hr. LED life, 90 CRI



Satin Nickel

		LED	Source Lumens	CCT	H	W	D
<b>Satin Nickel</b>	<b>Oakley Bronze</b>						
NLS6121400L27UDSN	NLS6121400L27UDKB	15W	1400	2700K	12-5/8"	6-1/2"	3-7/8"
NLS6121400L30UDSN	NLS6121400L30UDKB	15W	1400	3000K	12-5/8"	6-1/2"	3-7/8"
NLS6191400L27UDSN	NLS6191400L27UDKB	15W	1400	2700K	19-1/2"	6-1/2"	3-7/8"
NLS6191400L30UDSN	NLS6191400L30UDKB	15W	1400	3000K	19-1/2"	6-1/2"	3-7/8"
NLS6192100L27UDSN	NLS6192100L27UDKB	23W	2100	2700K	19-1/2"	6-1/2"	3-7/8"
NLS6192100L30UDSN	NLS6192100L30UDKB	23W	2100	3000K	19-1/2"	6-1/2"	3-7/8"

LED DIM ADA




## Companion



SCONCE



Red



Amber



Blue



White

# BELLA

- Die-cast metal backplate
- Hand blown glass diffuser


## LED

- 50,000 hr. LED life, available in 500 lumens (6W), 90 CRI

7-7/8" H x 4-1/2" W x 5-5/8" D

Series	Source Lumens	LED	CCT	Driver	Finish	Glass
BESL	500	L	30 3000K	D1 Voltage (120V TRIAC Dimming) D2 Voltage (120-277V 0-10V Dimming)	SN Satin Nickel	AM Amber BU Blue RD Red WH White

Example: BESL500L30D1SNAM



Companion





# LAVEER

- Die-cast metal backplate
- Hand blown glass diffuser


## LED

- 50,000 hr. LED life, available in 500 lumens (6W), 90 CRI

8-1/2" H x 4-5/8" W x 6-1/4" D

Series	Source Lumens	LED	CCT	Driver	Finish	Glass
LASL	500	L	30 3000K	D1 Voltage (120V TRIAC Dimming) D2 Voltage (120-277V 0-10V Dimming)	SN Satin Nickel	AM Amber BU Blue GR Green WH White

Example: LASL500L30D2SNBU



Companion







Satin Nickel



Oil-Rubbed Bronze

# MONTROSE

- Single or double die-cast metal arm
- Cream linen shade

## FLUORESCENT


- 120V electronic socket ballast
- Lamps not included

### Single Arm

Satin Nickel	Oil-Rubbed Bronze	Qty.	Lamp	H	W	D
MNS0818118QENSN	MNS0818118QENRB	1	18W CFQ 4-Pin	18-1/8"	7-1/2"	4"

### Double Arm

MNS1318218QENSN	MNS1318218QENRB	2	18W CFQ 4-Pin	18-1/8"	12-1/2"	4"
-----------------	-----------------	---	---------------	---------	---------	----







# TAYLOR

- Single or double die-cast metal arm
- Linen acrylic shade
- White acrylic top and bottom diffuser

## LED

- 120-277V universal-voltage driver
- Compatible with residential (TRIAC/ELV) and commercial (0-10V) dimmers
- TRIAC and ELV dimming only at 120V
- 50,000 hr. LED life, 90 CRI

### Single Arm

Polished Chrome	LED	Source Lumens	CCT	H	W	D
TAS613700L27UDPCLA	7W	700	2700K	13-1/2"	6-1/8"	4"
TAS613700L30UDPCLA	7W	700	3000K	13-1/2"	6-1/8"	4"

### Double Arm

TAS13131400L27UDPCLA	15W	1400	2700K	13-1/2"	12-5/8"	4"
TAS13131400L30UDPCLA	15W	1400	3000K	13-1/2"	12-5/8"	4"



## FLUORESCENT


- 120-277V universal-voltage ballast
- Lamp(s) not included

### Single Arm


Polished Chrome	Qty.	Lamp	H	W	D
TAS0613113QMPVCLA	1	13W CFQ 4-Pin	13-1/2"	6-1/8"	4"

### Double Arm

TAS1313213QMPVCLA	2	13W CFQ 4-Pin	13-1/2"	12-5/8"	4"
-------------------	---	---------------	---------	---------	----



### Companion






# DELANY

- Die-cast metal decorative accents
- Perforated top and bottom metal diffuser
- Faceted white acrylic front diffuser

## LED

- 120-277V universal-voltage driver
- Compatible with residential (TRIAC/ELV) and commercial (0-10V) dimmers
- TRIAC and ELV dimming only at 120V
- 50,000 hr. LED life, 90 CRI

Satin Nickel	Source			H	W	D
	LED	Lumens	CCT			
MIDS13151400L27UDSN	15W	1400	2700K	15"	13"	3-7/8"
MIDS13151400L30UDSN	15W	1400	3000K	15"	13"	3-7/8"





# RESTORATION

- Die-cast metal decorative accents
- Opal glass diffuser
- Open top and bottom

## LED

- 120-277V universal-voltage driver
- Compatible with residential (TRIAC/ELV) and commercial (0-10V) dimmers
- TRIAC and ELV dimming only at 120V
- 50,000 hr. LED life, 90 CRI

Oil-Rubbed Bronze	LED	Source Lumens	CCT	H	W	D
RES12111400L27UDRB	15W	1400	2700K	11-3/4"	12-3/4"	4"
RES12111400L30UDRB	15W	1400	3000K	11-3/4"	12-3/4"	4"

LED

DIM

ADA

Companion



# ARIA

- Die-cast metal end cap
- Frosted white glass diffuser


## FLUORESCENT

- 120V electronic socket ballast
- Lamps not included

Satin Nickel	Oil-Rubbed Bronze	Qty.	Lamp	H	W	D
ARS118SNEC*	ARS118RBEC*	1	18W CFQ 4-Pin	11"	4-3/8"	4"
ARS126SNEC	ARS126RBEC	1	26W CFQ 4-Pin	11"	4-3/8"	4-1/2"



Oil-Rubbed Bronze



## Companion





# LANCET


- Decorative finials
- White glass diffuser

## LED

- 120-277V universal-voltage driver
- Compatible with residential (TRIAC/ELV) and commercial (0-10V) dimmers
- TRIAC and ELV dimming only at 120V
- 50,000 hr. LED life, 90 CRI

White	LED	Source Lumens	CCT	H	W	D
LCS6151400L27UDWH	15W	1400	2700K	15"	5-7/8"	3-7/8"
LCS6151400L30UDWH	15W	1400	3000K	15"	5-7/8"	3-7/8"

**LED** **DIM** **ADA**





# TRILLIUM


- Decorative metal bands
- White acrylic diffuser, open top and bottom

## LED

- 120-277V universal-voltage driver
- Compatible with residential (TRIAC/ELV) and commercial (0-10V) dimmers
- TRIAC and ELV dimming only at 120V
- 50,000 hr. LED life, 90 CRI

Satin Nickel	LED	Source Lumens	CCT	H	W	D
TRS7121400L27UDSN	15W	1400	2700K	12-7/8"	7-7/8"	4"
TRS7121400L30UDSN	15W	1400	3000K	12-7/8"	7-7/8"	4"
TRS7122100L27UDSN	23W	2100	2700K	12-7/8"	7-7/8"	4"
TRS7122100L30UDSN	23W	2100	3000K	12-7/8"	7-7/8"	4"

LED DIM ADA





Satin Nickel

# BRIO

- Decorative metal bands
- White acrylic diffuser, open top and bottom

## LED


- 120-277V universal-voltage driver
- Compatible with residential (TRIAC/ELV) and commercial (0-10V) dimmers
- TRIAC and ELV dimming only at 120V
- 50,000 hr. LED life, 90 CRI

Satin Nickel	Oil-Rubbed Bronze	LED	Source Lumens	CCT	H	W	D
BRS7181400L27UDSN	BRS7181400L27UDRB	15W	1400	2700K	18"	7-1/4"	4"
BRS7181400L30UDSN	BRS7181400L30UDRB	15W	1400	3000K	18"	7-1/4"	4"
BRS7182100L27UDSN	BRS7182100L27UDRB	23W	2100	2700K	18"	7-1/4"	4"
BRS7182100L30UDSN	BRS7182100L30UDRB	23W	2100	3000K	18"	7-1/4"	4"



Oil-Rubbed Bronze

**LED** **DIM** **ADA**



SCONCE



Oakley Bronze

# ALGIERS

- Metal ends
- Linen acrylic front diffuser
- White acrylic top and bottom diffuser
- Vertical or horizontal mount

## LED

- 120-277V universal-voltage driver
- Compatible with residential (TRIAC/ELV) and commercial (0-10V) dimmers
- TRIAC and ELV dimming only at 120V
- 50,000 hr. LED life, 90 CRI




Satin Nickel

		Oakley Bronze	LED	Source Lumens	CCT	H	W	D
Satin Nickel	ALS16061400L27UDSN	ALS16061400L27UDKB	13W	1400	2700K	6"	15-1/2"	4"
	ALS16061400L30UDSN	ALS16061400L30UDKB	13W	1400	3000K	6"	15-1/2"	4"



Companion








# IDEAL

- Metal ends
- White glass diffuser
- White acrylic bottom

## LED

- 120-277V universal-voltage driver
- Compatible with residential (TRIAC/ELV) and commercial (0-10V) dimmers
- TRIAC and ELV dimming only at 120V
- 50,000 hr. LED life, 90 CRI

Satin Nickel	LED	Source Lumens	CCT	H	W	D
IDS09101400L30UDSN	15W	1400	3000K	10"	8-3/4"	3-1/2"



Companion





# MONROE

- Metal housing
- Enclosed frosted white glass diffuser

## LED

- 120V TRIAC dimmable
- 50,000 hr. life, 80 CRI, 3000K

Satin Nickel	LED	Source Lumens	H	W	D
MRS44500L30D1SN	6W	500	4-5/8"	4-5/8"	4"



Companion





# RIO

- Cylindrical metal housing
- White acrylic diffuser

## LED

- 120V TRIAC dimmable
- 50,000 hr. LED life, 90 CRI

	LED	Source Lumens	CCT	H	W	D
<b>Satin Nickel</b> RIS21800L30D1SN	8W	800	3000K	21-1/2"	4"	3-5/8"
RIS321600L30D1SN	16W	1600	3000K	32-1/2"	4"	3-5/8"



Companion






# BILBAO

- Aluminum bands
- White glass diffuser

## LED

- 120-277V universal-voltage driver
- Compatible with residential (TRIAC/ELV) and commercial (0-10V) dimmers
- TRIAC and ELV dimming only at 120V
- 50,000 hr. LED life, 90 CRI

Satin Aluminum	LED	Source Lumens	CCT	H	W	D
BBS1011400L27UDSA	15W	1400	2700	11-1/8"	10"	4"
BBS1011400L30UDSA	15W	1400	3000	11-1/8"	10"	4"



Companion






# CENTURY

- Die-cast metal accents
- White glass diffuser

## LED

- 120-277V universal-voltage driver
- Compatible with residential (TRIAC/ELV) and commercial (0-10V) dimmers
- TRIAC and ELV dimming only at 120V
- 50,000 hr. LED life, 90 CRI

Polished Chrome	LED	Source Lumens	CCT	H	W	D
CES11121400L27UDPC	15W	1400	2700K	12"	10-7/8"	4"
CES11121400L30UDPC	15W	1400	3000K	12"	10-7/8"	4"



Companion



## FLUORESCENT

- 120-277V universal-voltage ballast
- Lamps not included

Polished Chrome	Qty.	Lamp	H	W	D
CES1112213QMVPC	2	13W CFQ 4-Pin	12"	10-7/8"	4"
CES1112218QMVPC	2	18W CFQ 4-Pin	12"	10-7/8"	4"
CES1112226QMVPC	2	26W CFQ 4-Pin	12"	10-7/8"	4"





Satin Nickel



# FUSION

- Metal accent trim band
- White textured glass diffuser with open top
- White glass bottom diffuser


## LED

- 120-277V universal-voltage driver
- Compatible with residential (TRIAC/ELV) and commercial (0-10V) dimmers
- TRIAC and ELV dimming only at 120V
- 50,000 hr. LED life, 90 CRI



Oil-Rubbed Bronze

Satin Nickel	Oil-Rubbed Bronze	LED	Source Lumens	CCT	H	W	D
FUS10111400L27UDSN	FUS10111400L27UDRB	15W	1400	2700K	11-1/4"	9-7/8"	4"
FUS10111400L30UDSN	FUS10111400L30UDRB	15W	1400	3000K	11-1/4"	9-7/8"	4"



## Companion





# LASALLE


- Decorative metal accents
- Enclosed top and bottom
- White acrylic front and top diffuser

## LED

- 120-277V universal-voltage driver
- Compatible with residential (TRIAC/ELV) and commercial (0-10V) dimmers
- TRIAC and ELV dimming only at 120V
- 50,000 hr. LED life, 90 CRI

Satin Nickel	LED	Source Lumens	CCT	H	W	D
LAS6261400L27UDSN	15W	1400	2700K	27-7/8"	5-1/2"	4"
LAS6261400L30UDSN	15W	1400	3000K	27-7/8"	5-1/2"	4"
LAS6262100L27UDSN	23W	2100	2700K	27-7/8"	5-1/2"	4"
LAS6262100L30UDSN	23W	2100	3000K	27-7/8"	5-1/2"	4"

LED DIM ADA



## FLUORESCENT

- 120-277V universal-voltage ballast
- Lamps not included

Satin Nickel	Qty.	Lamp	H	W	D
LAS0626214T5MVSN	2	14W T5	27-7/8"	5-1/2"	4"





# UNITY


- Decorative finials
- White glass diffuser

## LED

---

- 120V TRIAC dimmable
- 50,000 hr. LED life, 80 CRI

Brushed Nickel	LED	Source Lumens	CCT	H	W	D
USS50030LBNWS	6W	500	3000K	8-1/4"	8"	4"





VANITY



# NOVARA

- Metal accents
- White acrylic diffuser
- Horizontal or vertical mount

## LED

- 120V TRIAC dimmable
- 50,000 hr. LED life, 90 CRI

Satin Nickel	LED	Source Lumens	CCT	L	H	D
NVV5252400L30D1SN	31W	2400	3000K	25"	4-1/2"	3-5/8"
NVV5373600L30D1SN	46.5W	3600	3000K	37"	4-1/2"	3-5/8"
NVV5494800L30D1SN	62W	4800	3000K	49"	4-1/2"	3-5/8"



Companion





Satin Nickel

# ARDEN

- Walnut finish
- Clear outer glass cylinder
- White inner glass cylinder
- Mount up or down

## LED

- 120V TRIAC dimmable
- 50,000 hr. LED life, 90 CRI



Oil-Rubbed Bronze


### Satin Nickel

RNV15081200L30D1SN  
RNV24081800L30D1SN  
RNV30082400L30D1SN

### Oil-Rubbed Bronze

RNV15081200L30D1RB  
RNV24081800L30D1RB  
RNV30082400L30D1RB

LED	Source Lumens	CCT	L	H	D
15.5W	1200	3000K	15-1/2"	8-3/8"	4"
22.5W	1800	3000K	23-3/4"	8-3/8"	4"
30W	2400	3000K	30"	8-3/8"	4"



### Companion





# SINCLAIR

- Metal housing
- Frosted white acrylic diffuser
- Horizontal or vertical mount

## LED

- 120-277V universal-voltage, 0-10V dimming
- 50,000 hr. LED life, 90 CRI

Satin Nickel	LED	Source Lumens	CCT	L	H	D
SNV24052000L30D2SN	26W	2000	3000K	27"	4-5/8"	3"
SNV36053000L30D2SN	35W	3000	3000K	39"	4-5/8"	3"
SNV48054000L30D2SN	49W	4000	3000K	50-1/4"	4-5/8"	3"



Companion





Satin Nickel

# CHARLOTTE

- Perforated metal ends
- White acrylic diffuser
- Horizontal or vertical mount

## LED

- 120-277V universal-voltage, 0-10V dimming
- 50,000 hr. LED life, 90 CRI



Oil-Rubbed Bronze

Satin Nickel		Oil-Rubbed Bronze		LED	Source Lumens	CCT	L	H	D
CHV29052000L30D2SN	CHV29052000L30D2RB	26W	2000	3000K	29-1/4"	4-1/2"	3-3/8"		
CHV41053000L30D2SN	CHV41053000L30D2RB	35W	3000	3000K	41-1/4"	4-1/2"	3-3/8"		



Companion






Satin Nickel  
White/White

# CORTEZ

- Sheer organza fabric outer shade
- White linen inner shade with die-cast details
- White acrylic bottom diffuser



Oakley Bronze  
Bronze/White

## LED

- 50,000 hr. LED life, available in 1200 lumens (20W), 1800 lumens (30W) or 2400 lumens (40W), 90 CRI


24-1/4" L x 5" H x 4-3/4" D

37-1/4" L x 5" H x 4-3/4" D

50-1/4" L x 5" H x 4-3/4" D

Series	Size (Inches)		Source Lumens	LED	CCT	Driver	Finish	Shade-In-Shade
	L	H						
CZV	24	05	= 1200	L	30 3000K	D1 Voltage (120V TRIAC Dimming)	KB Oakley Bronze SN Satin Nickel	WHWH White/White BZWH Bronze/White
	37	05	= 1800					
	50	05	= 2400					

Example: CZV24051200L30D1KBBZWH



## Companion





# PACIFIC

- Metal ends
- White acrylic diffuser
- Horizontal or vertical mount

## LED

- 120-277V universal-voltage driver
- 50,000 hr. LED life, 80 CRI

Satin Nickel	LED	Source Lumens	CCT	L	H	D
PCV241700L30MVSN	17W	1700	3000K	24"	6"	3-1/8"
PCV362500L30MVSN	25W	2500	3000K	36"	6"	3-1/8"
PCV483400L30MVSN	34W	3400	3000K	48"	6"	3-1/8"





Satin Nickel

# ALGIERS

- Metal ends
- Linen acrylic front diffuser
- White acrylic top and bottom diffuser
- Horizontal or vertical mount



Oakley Bronze

## LED

- 120-277V universal-voltage, 0-10V dimming
- 50,000 hr. LED life, 90 CRI

		Source			L	H	D
Satin Nickel	Oakley Bronze	LED	Lumens	CCT			
ALV25052000L30SND2*	ALV25052000L30KBD2*	25W	2000	3000K	25-1/4"	5"	4"
ALV37053000L30SND2*	ALV37053000L30KBD2*	36W	3000	3000K	37-1/4"	5"	4"
ALV49054000L30SND2	ALV49054000L30KBD2	49W	4000	3000K	49-1/4"	5"	4-7/8"

**LED** **DIM** **ADA**\*



## Companion







VANITY



Satin Nickel

# ARIA

- Die-cast aluminum ends
- White acrylic diffuser
- Horizontal or vertical mount



Oil-Rubbed Bronze

## LED

- 120-277V universal-voltage driver
- 50,000 hr. LED life, 90 CRI

		Source			L	H	D
Satin Nickel	Oil-Rubbed Bronze	LED	Lumens	CCT			
ARV26041000L30MVSN	ARV26041000L30MVRB	20W	1000	3000K	26-1/4"	4"	4"
ARV38041400L30MVSN	ARV38041400L30MVRB	30W	1400	3000K	38"	4"	4"
ARV50042100L30MVSN	ARV50042100L30MVRB	40W	2100	3000K	50"	4"	4"



## Companion





# CENTURY

- Die-cast metal accents
- White acrylic diffuser
- Horizontal or vertical mount

## LED

- 120-277V universal-voltage, 0-10V dimming
- 50,000 hr. LED life, 90 CRI

Polished Chrome	LED	Source Lumens	CCT	L	H	D
CEV26062000L30D2PC	26W	2000	3000K	26-1/4"	6-1/4"	4-3/8"
CEV38063000L30D2PC	35W	3000	3000K	38-1/8"	6-1/4"	4-3/8"
CEV50064000L30D2PC	49W	4000	3000K	50"	6-1/4"	4-3/8"

**LED** **DIM**



Companion





# TAYLOR

- Metal backplate and arm
- White linen acrylic front diffuser
- Clear top and white bottom acrylic diffuser

## LED

- 120-277V universal-voltage, 0-10V dimming
- 50,000 hr. LED life, 90 CRI

Polished Chrome	LED	Source Lumens	CCT	L	H	D
TAV40063000L30D2	35W	3000	3000K	40-1/4"	6-1/4"	5-1/8"



Companion





# BILBAO

- Aluminum bands
- White acrylic diffuser

## LED

- 120-277V universal-voltage, 0-10V dimming
- 50,000 hr. LED life, 90 CRI

Satin Aluminum	LED	Source Lumens	CCT	L	H	D
BBV32052000L30D2SA	26W	2000	3000K	32-3/8"	4-1/2"	4-1/2"
BBV44053000L30D2SA	35W	3000	3000K	44-3/8"	4-1/2"	4-1/2"



## Companion





# FUSION

- Die-cast metal ends and center accent
- White textured glass diffuser
- Horizontal or vertical mount


## LED

- 120-277V universal-voltage, 0-10V dimming
- 50,000 hr. LED life, 90 CRI



2 ft.

Satin Nickel	LED	Source Lumens	CCT	L	H	D
FUV26042000L30SND2	26W	2000	3000K	25-3/4"	5-3/8"	4-3/8"
FUV38043000L30SND2	35W	3000	3000K	37-3/4"	5-3/8"	4-3/8"
FUV50044000L30SND2	49W	4000	3000K	50"	5-3/8"	4-3/8"



## Companion





# VERNON


- Metal backplate
- White glass diffusers
- Mount up or down

## FLUORESCENT

- GU24 self-ballast lamps (not included)



Satin Nickel	Qty.	Lamp	L	H	D
VNV313SNSCT	3	13W GU24	17-1/2"	8"	5"
VNV513SNSCT	5	13W GU24	29-1/2"	8"	5"





# RIO

- Metal housing
- Double white acrylic diffuser
- Horizontal or vertical mount

## LED

- 120V TRIAC dimmable
- 50,000 hr. LED life, 90 CRI

Satin Nickel	LED	Source Lumens	CCT	L	H	D
RIS321600L30D1SN	16W	1600	3000K	32-1/2"	4"	3-5/8"



Companion







VANITY



Satin Nickel

# EVOLUTION

- Metal ends
- White acrylic diffuser
- Horizontal or vertical mount

## FLUORESCENT

- 120V electronic ballast
- Lamps not included



Oil-Rubbed Bronze

Satin Nickel	Oil-Rubbed Bronze	Qty.	Lamp	H	L	D
EOV217SNR8	EOV217RBR8	2	F17T8	24-3/4"	5-3/4"	4-1/4"
EOV225SNR8	EOV225RBR8	2	F25T8	36-3/4"	5-3/4"	4-1/4"
EOV232SNR8	EOV232RBR8	2	F32T8	48-3/4"	5-3/4"	4-1/4"





Satin Nickel

# NOLAN

- Die-cast metal accents
- Clear outer glass
- White acrylic inner diffuser
- Horizontal or vertical mount

## FLUORESCENT

- 120-277V universal-voltage ballast
- Lamps not included



Oakley Bronze

Satin Nickel	Oakley Bronze	Qty.	Lamp	L	H	D
NLV214SNMV	NLV214RBMV	2	F14T5	25-3/4"	6-1/4"	4"
NLV221SNMV	NLV221RBMV	2	F21T5	37-3/4"	6-1/4"	4"
NLV228SNMV	NLV228RBMV	2	F28T5	49-3/4"	6-1/4"	4"



## Companion





# STRATUS

- White acrylic diffuser fully encloses housing
- Horizontal or vertical mount

## LED

- 120-277V universal-voltage, 0-10V dimming
- 50,000 hr. LED life, 90 CRI

White	LED	Source Lumens	CCT	L	H	D
V8PN26042000L30D2	26W	2000	3000K	26-3/4"	4-5/8"	4"
V8PN38043000L30D2	35W	3000	3000K	38-3/4"	4-5/8"	4"
V8PN50044000L30D2	49W	4000	3000K	50-3/4"	4-5/8"	4"



## FLUORESCENT

- 120V electronic ballast (R8)
- 120-277V universal-voltage ballast (MV)
- Lamps not included

White 120V	120-277V	Qty.	Lamp	L	H	D
V8PN217R8	V8PN217MV	2	F17T8	26-3/4"	4-5/8"	4"
V8PN225R8	V8PN225MV	2	F25T8	38-3/4"	4-5/8"	4"
V8PN232R8	V8PN232MV	2	F32T8	50-3/4"	4-5/8"	4"





Chrome

# VISTA

- Metal ends
- White acrylic diffuser
- Horizontal or vertical mount

## FLUORESCENT

- 120-277V universal-voltage ballast
- Lamps not included



White

Chrome	White	Qty.	Lamp	L	H	D
VSC217MV	VSW217MV	2	F17T8	24-1/4"	4-1/2"	4-1/2"
VSC225MV	VSW225MV	2	F25T8	36-1/4"	4-1/2"	4-1/2"
VSC232MV	VSW232MV	2	F32T8	48-1/4"	4-1/2"	4-1/2"





# ATWATER

- Metal ends
- Ribbed white acrylic diffuser
- Grounded convenience outlet and turn switch
- Horizontal or vertical mount

## FLUORESCENT

- 120V electronic ballast
- Lamps not included

White	Qty.	Lamp	L	H	D
ADWW217R8	2	F17T8	24-1/8"	3-3/8"	5-1/4"
ADWW225R8	2	F25T8	36-1/8"	3-3/8"	5-1/4"
ADWW232R8	2	F32T8	48-1/8"	3-3/8"	5-1/4"



# FIXED RAIL







# DISTRICT


- Clear outer glass
- White glass inner diffuser
- Heads swivel and pivot
- Ceiling or wall mount

## LED

- 120V TRIAC dimmable
- 50,000 hr. LED life, 90 CRI

Satin Nickel	LED	Source Lumens	CCT	L	W	H
DISF4400L30SN	25W	1600	3000K	36-1/2"	5-3/8"	7-7/8"

See page 135 for listing of compatible dimmers.







# GRAMERCY


- Two-tone finish
- Heads swivel and pivot
- Ceiling or wall mount

## LED

- 120V TRIAC dimmable
- 50,000 hr. LED life, 90 CRI

Satin Nickel	LED	Source Lumens	CCT	L	W	H
GRAF4400L30WH	25W	1600	3000K	36-1/2"	5-3/8"	7-7/8"

See page 135 for listing of compatible dimmers.





# CHAPPELLE

- Heads swivel and pivot
- Ceiling or wall mount


## LED

- 120V TRIAC dimmable
- 50,000 hr. LED life, 90 CRI



Satin Nickel	LED	Source Lumens	CCT	L	W	H
CHRF4400L30SN	25W	1600	3000K	36-5/8"	5-1/4"	7"

See page 135 for listing of compatible dimmers.





FIXED RAIL

**COMPATIBLE DIMMERS**

Brand	Series	Model#	Brand	Series	Model#
Lutron®	Maestro	MACL-153M	Leviton®	Decora	DLS06-1LZ
	SkyLark Contour	CTCL-153P		Iluma Tech	IPL06-10Z
	Caseta	PD-6WCL		Sure Slide	6672-1LW
			Sure Slide	6674-P0W	

Product can be dimmed down to 10% of full scale.



# METRO

- Frosted glass diffusers
- Heads swivel and pivot
- Ceiling or wall mount


## LED

- 120V TRIAC dimmable
- 50,000 hr. LED life, 90 CRI



Satin Nickel	LED	Source Lumens	CCT	L	W	H
MTRF4400L30SN	25W	1600	3000K	36-5/8"	5-15/16"	6-13/16"

See page 135 for listing of compatible dimmers.





# CORE

- Heads swivel and pivot
- Ceiling or wall mount

## LED

- 120V TRIAC dimmable
- 50,000 hr. LED life, 90 CRI

Satin Nickel	LED	Source Lumens	CCT	L	W	H
CRRF4400L30SN	25W	1600	3000K	36-3/8"	5-3/8"	6-1/4"
CRRF6400L30SN	42W	2400	3000K	55-1/8"	5-1/4"	7-1/2"


Polished Chrome	LED	Source Lumens	CCT	L	W	H
CRRF4400L30PC	25W	1600	3000K	36-3/8"	5-3/8"	6-1/4"



Polished Chrome

Satin Nickel

See page 135 for listing of compatible dimmers.



FIXED RAIL





# CANTRELL

- Heads swivel and pivot
- Ceiling or wall mount


## LED

- 120V TRIAC dimmable
- 50,000 hr. LED life, 90 CRI



Satin Nickel	LED	Source Lumens	CCT	L	W	H
CARF4400L30SN	25W	1600	3000K	36-5/8"	5-1/4"	5-5/8"


See page 135 for listing of compatible dimmers.





# CEILING





# BOON

- Metal housing
- Edge-lit light panel
- Low-profile design

## LED

- 120V TRIAC dimmable
- 50,000 hr. LED life, 90 CRI

White	LED	Source Lumens	CCT	DIA.	D
BOF121400L30D1WH	17.5W	1400	3000K	12"	4"
BOF162600L30D1WH	31W	2600	3000K	16"	4-1/2"

**LED** **DIM**



CEILING



Black/Gold



White/Black

# REVEAL

- Metal housing
- Edge-lit light panel
- Low profile design

## LED

- 120V TRIAC dimmable
- 50,000 hr. LED life, 90 CRI

		LED	Source Lumens	CCT	DIA.	D
<b>Black/Gold</b>	<b>White/Black</b>					
RVF121400L30D1BKGD	RVF121400L30D1WHBK	17.5W	1400	3000K	12"	2-3/4"
RVF162600L30D1BKGD	RVF162600L30D1WHBK	31W	2600	3000K	16"	3-1/4"





Chrome/Black



Satin Nickel/White

# ALTA

- Metal housing
- Edge-lit light panel
- Low profile design

## LED

- 120V TRIAC dimmable
- 50,000 hr. LED life, 90 CRI

		LED	Source Lumens	CCT	DIA.	D
<b>Black/Chrome</b>	<b>Satin Nickel/White</b>					
AAF121400L30D1BKPC	AAF121400L30D1SNWH	17.5W	1400	3000K	12"	2"
AAF162600L30D1BKPC	AAF162600L30D1SNWH	31W	2600	3000K	16"	2"





# SINCLAIR

- Metal housing
- Frosted white acrylic diffuser

## LED


- 120V TRIAC dimmable (D1)
- 120-277V universal-voltage driver, 0-10V dimming (D2)
- 50,000 hr. LED life, 90 CRI

Satin Nickel	LED	Source Lumens	CCT	L	W	D
SNF141400L30D1SN	15W	1400	3000K	14"	14"	4-1/2"
SNF141400L30D2SN	15W	1400	3000K	14"	14"	4-1/2"
SNF172400L30D1SN	24W	2400	3000K	17"	17"	4-1/2"
SNF172400L30D2SN	24W	2400	3000K	17"	17"	4-1/2"

**LED** **DIM**



Companion







Satin Nickel

# SLOANE

- Extruded metal frame
- Edge-lit light panel
- Low profile

## LED

- 120V TRIAC dimmable
- 50,000 hr. LED life, 90 CRI



White

		LED	Source Lumens	CCT	L	W	D
<b>Satin Nickel</b>	<b>White</b>						
SLF12121100L30D1SN	SLF12121100L30D1WH	18.5W	1100	3000K	15"	15"	2"
SLF12241800L30D1SN	SLF12241800L30D1WH	25.8W	1800	3000K	27"	15"	2"



Companion



Satin Nickel



# ZURICH

- Extruded metal frame
- Edge-lit light panel
- Low profile

## LED

- 120V TRIAC dimmable
- 50,000 hr. LED life, 90 CRI



White

			Source		L	W	D
		LED	Lumens	CCT			
<b>Satin Nickel</b>	<b>White</b>						
ZUF12121100L30D1SN	ZUF12121100L30D1WH	18.5W	1100	3000K	15"	15"	2-3/8"
ZUF12241800L30D1SN	ZUF12241800L30D1WH	26W	1800	3000K	27"	15"	2-3/8"



Companion





Satin Nickel

# ATLAS

- Extruded metal frame
- Edge-lit light panel
- Low profile

## LED

- 120V TRIAC dimmable
- 50,000 hr. LED life, 90 CRI



Oil-Rubbed Bronze

		LED	Source Lumens	CCT	L	W	D
<b>Satin Nickel</b>	<b>Oil-Rubbed Bronze</b>						
ATLF12121100L30D1SN	ATLF12121100L30D1RB	18.5W	1100	3000K	15"	15"	2"
ATLF12241800L30D1SN	ATLF12241800L30D1RB	26W	1800	3000K	27"	15"	2"



Companion





# SUTTON

- Metal housing
- White glass diffuser

## LED

- 120V TRIAC dimmable (D1)
- 120-277V universal-voltage driver, 0-10V dimming (D2)
- 50,000 hr. LED life, 90 CRI

Satin Nickel	LED	Source Lumens	CCT	DIA.	D
SUF151400L30D1SN	15W	1400	3000K	14-1/2"	4-1/2"
SUF151400L30D2SN	15W	1400	3000K	14-1/2"	4-1/2"
SUF182400L30D1SN	24W	2400	3000K	17-1/2"	4-3/4"
SUF182400L30D2SN	24W	2400	3000K	17-1/2"	4-3/4"





## AXEL

- Powder coated matte white metal housing
- Illuminated white frosted acrylic diffuser
- Ceiling or wall mount

### LED

- 120V TRIAC dimmable
- 50,000 hr. LED life, 90 CRI

White	LED	Source Lumens	CCT	DIA.	D
AXF06800L30D1WH	10W	800	3000K	6"	2"

**LED** **DIM** **ADA**



## MADDOX

- Powder coated matte white metal housing
- Illuminated white frosted acrylic diffuser
- Ceiling or wall mount

### LED

- 120V TRIAC dimmable
- 50,000 hr. LED life, 90 CRI

White	LED	Source Lumens	CCT	L	W	D
MAF606800L30D1WH	10W	800	3000K	6"	6"	2"

**LED** **DIM** **ADA**





Espresso/Jute

# APEX

- Solid wood accent detail
- LumaFuse™ laminated fabric/acrylic shade
- White bottom acrylic diffuser
- Options: Semi-flush mounting, battery back-up

## LED

- 50,000 hr. LED life, available in 1400 lumens (15W), 2400 lumens (24W) or 3200 lumens (35W), 90 CRI





Weathered Gray/Linen White

### With Wood Accent

- 12-1/4" DIA. x 3-1/2" D
- 15" DIA. x 3-1/2" D
- 19" DIA. x 3-1/2" D
- 14-1/4" DIA. x 4-1/4" D
- 17" DIA. x 4-1/4" D
- 21-1/4" DIA. x 4-1/4" D

Series	Size (Inches)		LED	CCT	Driver	Wood Finish	Shade	Options
	DIA.	Source Lumens						
APF	12	= 1400	L	27 2700K	D1 Voltage (120V TRIAC Dimming) D2 Voltage (120-277V 0-10V Dimming)	ES Espresso WG Weathered Grey	JT Jute LW Linen White	Blank None BB Battery Backup SF Semi-Flush
	15	= 2400		30 3000K				
	19	= 3200						

Example: APF152400L30D2ES-LWSF



### Companion





Oakley Bronze  
Bronze/White

# CORTEZ

- Sheer organza fabric outer shade
- White linen inner shade
- White acrylic bottom diffuser



## LED

- 50,000 hr. LED life, available in 2400 lumens (24W), 3200 lumens (35W) or 4400 lumens (40W), 90 CRI

- 18" DIA. x 6-5/8" D
- 24" DIA. x 6-5/8" D
- 30" DIA. x 6-5/8" D

Series	Size (Inches)		LED	CCT	Driver	Finish	Shade-In-Shade
	DIA.	Source Lumens					
CZF	18	= 2400	L	30 3000K	D1 Voltage (120V TRIAC Dimming) D2 Voltage (120-277V 0-10V Dimming)	KB Oakley Bronze SN Satin Nickel	WHWH White/White BZWH Bronze/White
	24	= 3200					
	30	= 4400					

Example: CZF182400L30D2KB-BZWH



## Companion





# MONTCLAIR

- LumaFuse™ laminated fabric/acrylic shade
- Stepped white acrylic bottom diffuser
- Options: Semi-flush mounting, battery back-up

## LED

- 50,000 hr. LED life, available in 1400 lumens (15W), 2400 lumens (25W) or 3200 lumens (35W), 90 CRI

12-1/4" DIA. x 3-3/4" D


15" DIA. x 4-3/4" D

19-1/4" DIA. x 5-1/2" D



Series	Size (Inches)		LED	CCT	Driver	Shade	Options
	DIA.	Source Lumens					
MCF	12	= 1400	L	27 2700K	D1 Voltage (120V TRIAC Dimming) D2 Voltage (120-277V 0-10V Dimming)	BK Black	Blank None BB Battery Backup SF Semi-Flush
	15	= 2400		30 3000K			
	19	= 3200					

Example: MCF193200L27D1-BK



Companion







Chocolate/Jute

# EDEN

- LumaFuse™ laminated fabric/acrylic shade with wood veneer trim detail
- White bottom acrylic diffuser

## LED

- 50,000 hr. LED life, available in 1400 lumens (15W), 2400 lumens (24W) or 3200 lumens (35W), 90 CRI

12-1/4" L x 12-1/4" W x 4-3/4" H

15" L x 15" W x 4-3/4" H

19-1/4" L x 19-1/4" W x 4-3/4" H


Series	Size (Inches)		LED	CCT	Driver	Wood Finish	Shade
	DIA.	Source Lumens					
EDF	12	= 1400	L	27 2700K	D1 Voltage (120V TRIAC Dimming) D2 Voltage (120-277V 0-10V Dimming)	CV Chocolate Oak Veneer GV Grey Veneer	JT Jute LW Linen White
	15	= 2400		30 3000K			
	19	= 3200					

Example: EDF121400L30D1CV-JT



Grey/Linen White

CEILING





Linen White

# SANIBEL

- LumaFuse™ laminated fabric/acrylic shade
- White bottom acrylic inner diffuser
- Options: Semi-flush mounting, battery back-up

## LED

- 50,000 hr. LED life, available in 1400 lumens (15W), 2400 lumens (24W) or 3200 lumens (35W), 90 CRI


- 16" DIA. x 5-5/8" D
- 18" DIA. x 5-5/8" D
- 23-1/4" DIA. x 5-5/8" D



Jute

Series	Size (Inches)		LED	CCT	Driver	Shade	Options
	DIA.	Source Lumens					
SAF	16	= 1400	L	27	2700K	JT Jute LW Linen White	Blank None BB Battery Backup SF Semi-Flush
	18	= 2400		30	3000K		
	23	= 3200					

Example: SAF232400L30D1-JTBB





Jute

# ANTON

- LumaFuse™ laminated fabric/acrylic shade
- White bottom acrylic diffuser
- Options: Semi-flush mounting, battery back-up

## LED

- 50,000 hr. LED life, available in 1400 lumens (15W), 2400 lumens (24W) or 3200 lumens (35W), 90 CRI

12-1/4" DIA. x 4-3/4" D

15" DIA. x 5-1/2" D

19-1/4" DIA. x 5-1/2" D




Series	Size (Inches)		LED L	CCT	Driver
	DIA.	Source Lumens			
ANF	12	= 1400	L	27 2700K	D1 Voltage (120V TRIAC Dimming) D2 Voltage (120-277V 0-10V Dimming)
	15	= 2400		30 3000K	
	19	= 3200			



Linen White

- |  |   |
|--|---|
| <ul style="list-style-type: none"> <li>• Shade</li> <li>JT Jute</li> <li>LW Linen White</li> </ul> | <ul style="list-style-type: none"> <li>• Options</li> <li>Blank None</li> <li>BB Battery Backup</li> <li>SF Semi-Flush</li> </ul> |
|--|---|

Example: ANF121400L30D2-LW



Companion





# WILLOW

- LumaFuse™ laminated veneer/acrylic shade
- White bottom acrylic diffuser
- Options: Semi-flush mounting, battery back-up

## LED


- 50,000 hr. LED life, available in 1400 lumens (15W), 2400 lumens (24W) or 3200 lumens (35W), 90 CRI

12-1/4" DIA. x 4-7/8" D  
 15" DIA. x 4-7/8" D  
 19-1/4" DIA. x 4-7/8" D



Series	Size (Inches)		LED	CCT	Driver	Color	Options
	DIA.	Source Lumens					
WLF	12	= 1400	L	27 2700K	D1 Voltage (120V TRIAC Dimming) D2 Voltage (120-277V 0-10V Dimming)	GV Grey Veneer	Blank None BB Battery Backup SF Semi-Flush
	15	= 2400		30 3000K			
	19	= 3200					

Example: WLF152400L30D2-GVSF



Companion





Linen White

# OSLO

- LumaFuse™ laminated fabric/acrylic shade
- White domed bottom acrylic diffuser
- Options: Semi-flush mounting, battery back-up



## LED

- 50,000 hr. LED life, available in 1400 lumens (15W), or 2400 lumens (35W), 90 CRI

17" DIA. x 4-1/2" D  
24" DIA. x 5-3/4" D

Series	Size (Inches)		LED	CCT	Driver	Shade	Options
	DIA.	Source Lumens					
OSF	17	= 1400	L	27 2700K	D1 Voltage (120V TRIAC Dimming) D2 Voltage (120-277V 0-10V Dimming)	JT Jute LW Linen White	Blank None BB Battery Backup SF Semi-Flush
	24	= 2400		30 3000K			

Example: OSF171400L27D2-LWBB



Companion



Jute



Oakley Bronze



# NOLAN

- Die-cast metal accents
- Clear outer acrylic diffuser
- White acrylic inner diffuser

## LED

- 120V TRIAC dimmable (D1)
- 120-277V universal-voltage driver, 0-10V dimming (D2)
- 50,000 hr. LED life, 90 CRI



Satin Nickel

Satin Nickel	Oakley Bronze	LED	Source Lumens	CCT	DIA.	D
NLF162400L30D1SN	NLF162400L30D1KB	24W	2400	3000K	16-1/8"	3-1/2"
NLF162400L30D2SN	NLF162400L30D2KB	24W	2400	3000K	16-1/8"	3-1/2"

**LED** **DIM**



## Companion





Oakley Bronze

# ALGIERS

- Decorative metal trim ends
- Linen acrylic diffuser

## LED

- 120V TRIAC dimmable (D1)
- 120-277V universal-voltage driver, 0-10V dimming (D2)
- 50,000 hr. LED life, 90 CRI



Satin Nickel

Satin Nickel		Oakley Bronze		LED	Source Lumens	CCT	L	W	D
ALF162400L30D1SNLA		ALF162400L30D1KBLA		24W	2400	3000K	16-1/4"	16-1/4"	3"
ALF162400L30D2SNLA		ALF162400L30D2KBLA		24W	2400	3000K	16-1/4"	16-1/4"	3"

**LED** **DIM**



## Companion





# LYON

- Powder coated matte white metal housing
- Illuminated outer white frosted acrylic diffuser
- Ceiling or wall mount

## LED

- 120V TRIAC dimmable
- 50,000 hr. LED life, 90 CRI

White	LED	Source Lumens	CCT	DIA.	D
LYF10800L30D1WH	10W	800	3000K	10"	2"
LYF161900L30D1WH	18W	1900	3000K	16"	2"







# GENEVA

- Powder coated matte white metal housing
- Illuminated outer white frosted acrylic diffuser
- Ceiling or wall mount

## LED

- 120V TRIAC dimmable
- 50,000 hr. LED life, 90 CRI

White	LED	Source Lumens	CCT	L	W	D
GAF101300L30D1WH	12W	1300	3000K	10"	10"	2"
GAF162300L30D1WH	17W	2300	3000K	16"	16"	2"





# DELANY

- Die-cast metal accents
- Faceted white acrylic side diffuser
- White acrylic bottom diffuser

## LED


- 120V TRIAC dimmable (D1)
- 120-277V universal-voltage driver, 0-10V dimming (D2)
- 50,000 hr. LED life, 90 CRI

Satin Nickel	LED	Source Lumens	CCT	DIA.	D
MIDF162400L30D1SN	24W	2400	3000K	16-1/4"	5-3/4"
MIDF162400L30D2SN	24W	2400	3000K	16-1/4"	5-3/4"
MIDF222400L30D1SN	24W	2400	3000K	22-1/4"	5-3/4"
MIDF222400L30D2SN	24W	2400	3000K	22-1/4"	5-3/4"
MIDF223200L30D1SN	35W	3200	3000K	22-1/4"	5-1/2"
MIDF223200L30D2SN	35W	3200	3000K	22-1/4"	5-1/2"

## FLUORESCENT

- 120-277V universal-voltage ballast
- Lamps not included

Satin Nickel	Qty.	Lamp	DIA.	D
MIDF313SNMV	3	13W CFQ 4-Pin	16-1/4"	5-3/4"
MIDF318SNMV	3	18W CFQ 4-Pin	16-1/4"	5-3/4"
MIDF413SNMV	4	13W CFQ 4-Pin	22-1/4"	5-1/2"
MIDF418SNMV	4	18W CFQ 4-Pin	22-1/4"	5-1/2"



Companion





# MONROE

- Die-cast metal finial
- White acrylic diffuser

## LED

- 120V TRIAC dimmable (D1)
- 120-277V universal-voltage driver, 0-10V dimming (D2)
- 50,000 hr. LED life, 90 CRI

Satin Nickel	LED	Source Lumens	CCT	L	W	D
MRF162400L30D1SN	24W	2400	3000K	16-1/8"	16-1/8"	3-1/4"
MRF162400L30D2SN	24W	2400	3000K	16-1/8"	16-1/8"	3-1/4"



Companion





Satin Nickel

# SHERIDAN

- White linen acrylic side shade in satin nickel or hardback linen shade in champagne
- White acrylic bottom diffuser


## LED

- 120V TRIAC dimmable (D1)
- 120-277V universal-voltage driver, 0-10V dimming (D2)
- 50,000 hr. LED life, 90 CRI



Champagne

Satin Nickel	Champagne	LED	Source Lumens	CCT	DIA.	D
SHC162400L30D1SN-LA	SHC162400L30D1AC	24W	2400	3000K	16"	6"
SHC162400L30D2SN-LA	SHC162400L30D2AC	24W	2400	3000K	16"	6"
SHC223200L30D1SN-LA	SHC223200L30D1AC	35W	3200	3000K	22"	6"
SHC223200L30D2SN-LA	SHC223200L30D2AC	35W	3200	3000K	22"	6"



Companion






# HUDSON

- Ornamental metal housing
- Linen acrylic side and bottom diffusers

## LED

- 120V TRIAC dimmable (D1)
- 120-277V universal-voltage driver, 0-10V dimming (D2)
- 50,000 hr. LED life, 90 CRI

Satin Nickel	LED	Source Lumens	CCT	DIA.	D
HZC162400L30D1SN	24W	2400	3000K	16"	6"
HZC162400L30D2SN	24W	2400	3000K	16"	6"
HZC223200L30D1SN	35W	3200	3000K	22"	6"
HZC223200L30D2SN	35W	3200	3000K	22"	6"





# TAYLOR

- Metal housing and finial
- White linen fabric side diffuser
- White acrylic bottom diffuser

## LED

- 120V TRIAC dimmable (D1)
- 120-277V universal-voltage driver, 0-10V dimming (D2)
- 50,000 hr. LED life, 90 CRI

Polished Chrome	LED	Source Lumens	CCT	L	W	D
TAF162400L30D1PC-LA	24W	2400	3000K	16-1/2"	16-1/2"	5-1/4"
TAF162400L30D2PC-LA	24W	2400	3000K	16-1/2"	16-1/2"	5-1/4"



Companion



Link up to eight fixtures from a single power source



CEILING




# RESTORATION

- Die-cast metal accents
- White glass diffuser

## LED

- 120V TRIAC dimmable (D1)
- 120-277V universal-voltage driver, 0-10V dimming (D2)
- 50,000 hr. LED life, 90 CRI

Oil-Rubbed Bronze	LED	Source Lumens	CCT	DIA.	D
REF131400L30D1RB	15W	1400	3000K	12-1/4"	4-7/8"
REF131400L30D2RB	15W	1400	3000K	12-1/4"	4-7/8"
REF162400L30D1RB	24W	2400	3000K	15-1/4"	4-7/8"
REF162400L30D2RB	24W	2400	3000K	15-1/4"	4-7/8"



Companion



## FLUORESCENT

- 120-277V universal-voltage ballast
- Lamps not included

Oil-Rubbed Bronze	Qty.	Lamp	DIA.	D
REF13213QMVRB	2	13W CFQ 4-Pin	12-1/4"	4-7/8"
REF16218QMVRB	2	18W CFQ 4-Pin	15-1/4"	4-7/8"
REF16226QMVRB	2	26W CFQ 4-Pin	15-1/4"	4-7/8"








# CENTURY

- Die-cast metal accents
- White glass diffuser

## LED

- 120V TRIAC dimmable (D1)
- 120-277V universal-voltage driver, 0-10V dimming (D2)
- 50,000 hr. LED life, 90 CRI

Polished Chrome	LED	Source Lumens	CCT	DIA.	D
CEF131400L30D1PC	15W	1400	3000K	12-5/8"	4-3/4"
CEF131400L30D2PC	15W	1400	3000K	12-5/8"	4-3/4"
CEF162400L30D1PC	24W	2400	3000K	15-5/8"	4-3/4"
CEF162400L30D2PC	24W	2400	3000K	15-5/8"	4-3/4"



Companion





# FUSION


- Metal trim bands
- White textured glass side diffuser
- Smooth white glass bottom diffuser

## LED

- 120V TRIAC dimmable (D1)
- 120-277V universal-voltage driver, 0-10V dimming (D2)
- 50,000 hr. LED life, 90 CRI

Satin Nickel	LED	Source Lumens	CCT	DIA.	D
FUF131400L30D1SN	15W	1400	3000K	12-1/2"	4-3/4"
FUF131400L30D2SN	15W	1400	3000K	12-1/2"	4-3/4"
FUF162400L30D1SN	24W	2400	3000K	15-1/2"	4-3/4"
FUF162400L30D2SN	24W	2400	3000K	15-1/2"	4-3/4"

**LED** **DIM**



Companion






# BILBAO

- Linear aluminum bands
- White glass diffuser

## LED

- 120V TRIAC dimmable (D1)
- 120-277V universal-voltage driver, 0-10V dimming (D2)
- 50,000 hr. LED life, 90 CRI

Satin Aluminum	LED	Source Lumens	CCT	DIA.	D
BBF131400L30D1SA	15W	1400	3000K	13-1/4"	5"
BBF131400L30D2SA	15W	1400	3000K	13-1/4"	5"
BBF162400L30D1SA	24W	2400	3000K	16-1/2"	4-1/2"
BBF162400L30D2SA	24W	2400	3000K	16-1/2"	4-1/2"



Companion



CEILING



# CARLISLE

- Metal trim bands
- White acrylic diffuser
- Option: battery back-up (add BB to end of model #)

## LED

- 120V TRIAC dimmable
- 50,000 hr. LED life, 90 CRI




### Flush Mount

Satin Nickel	LED	Source Lumens	CCT	DIA.	D
CAF121200L27D1	12W	1200	2700K	12"	3-1/2"
CAF121200L30D1	12W	1200	3000K	12"	3-1/2"
CAF142400L27D1	27W	2400	2700K	14"	3-1/2"
CAF142400L30D1	27W	2400	3000K	14"	3-1/2"
CAF243100L27D1	35W	3100	2700K	24"	3-1/2"
CAF243100L30D1	35W	3100	3000K	24"	3-1/2"

### Semi-Flush Mount

Satin Nickel	LED	Source Lumens	CCT	DIA.	D
CAC121200L27D1	12W	1200	2700K	12"	3-1/2"
CAC121200L30D1	12W	1200	3000K	12"	3-1/2"
CAC142400L27D1	27W	2400	2700K	14"	3-1/2"
CAC142400L30D1	27W	2400	3000K	14"	3-1/2"
CAC243100L27D1	35W	3100	2700K	24"	3-1/2"
CAC243100L30D1	35W	3100	3000K	24"	3-1/2"





White

# CAPRI

- Metal trim band
- White acrylic diffuser

## LED

- 120V TRIAC dimmable
- 50,000 hr. LED life, 90 CRI



Brushed Nickel

CEILING

White	Brushed Nickel	LED	Source Lumens	CCT	DIA.	D
CFF091100L27D1WH	CFF091100L27D1BN	12W	1100	2700K	9-9/16"	2-3/8"
CFF091100L30D1WH	CFF091100L30D1BN	12W	1100	3000K	9-9/16"	2-3/8"
CFF111600L27D1WH	CFF111600L27D1BN	17W	1600	2700K	11"	3"
CFF111600L30D1WH	CFF111600L30D1BN	17W	1600	3000K	11"	3"
CFF142400L27D1WH	CFF142400L27D1BN	27W	2400	2700K	14"	3-7/16"
CFF142400L30D1WH	CFF142400L30D1BN	27W	2400	3000K	14"	3-7/16"
CFF193100L27D1WH	CFF193100L27D1BN	35W	3100	2700K	19"	4-3/16"
CFF193100L30D1WH	CFF193100L30D1BN	35W	3100	3000K	19"	4-3/16"






# IDEAL

- Metal trim band
- White acrylic diffuser

## LED

- 120-277V universal-voltage ballast
- 50,000 hr. LED life, 80 CRI

<b>Satin Nickel</b>	<b>LED</b>	<b>Source Lumens</b>	<b>CCT</b>	<b>L</b>	<b>W</b>	<b>D</b>
PIDF172900L40MVSN	32W	2900	4000K	32"	17"	4"



Companion





Satin Nickel

# COVINA

- Metal trim bands
- White acrylic diffuser


## LED

- 120V TRIAC dimmable
- 50,000 hr. LED life, 90 CRI



Oil-Rubbed Bronze

Satin Nickel	Oil-Rubbed Bronze	LED	Source Lumens	CCT	L	W	D
CVF324400L30D1SN	CVF324400L30D1RB	45W	4400	3000K	32-3/8"	17"	4-3/8"







# CAMDEN

- White acrylic diffuser
- Option: battery back-up (add BB to end of model #)

## LED

- 120V TRIAC dimmable
- 50,000 hr. LED life, 90 CRI

Satin Nickel	LED	Source Lumens	CCT	DIA.	D
CMF091100L27D1	12W	1100	2700K	9"	3-3/4"
CMF091100L30D1	12W	1100	3000K	9"	3-3/4"
CMF111600L27D1	17W	1600	2700K	11"	3-3/4"
CMF111600L30D1	17W	1600	3000K	11"	3-3/4"
CMF142400L27D1	27W	2400	2700K	14"	3-3/4"
CMF142400L30D1	27W	2400	3000K	14"	3-3/4"
CMF193100L27D1	35W	3100	2700K	19"	3-3/4"
CMF193100L30D1	35W	3100	3000K	19"	3-3/4"



# CARTER

- White acrylic diffuser

## LED

- 120V TRIAC dimmable
- 50,000 hr. LED life, 90 CRI

White	LED	Source Lumens	CCT	L	W	D
CSF101100L27D1	12W	1100	2700K	10"	10"	2-1/2"
CSF101100L30D1	12W	1100	3000K	10"	10"	2-1/2"
CSF121600L27D1	17W	1600	2700K	12"	12"	2-1/2"
CSF121600L30D1	17W	1600	3000K	12"	12"	2-1/2"
CSF142400L27D1	27W	2400	2700K	14"	14"	2-1/2"
CSF142400L30D1	27W	2400	3000K	14"	14"	2-1/2"
CSF193100L27D1	35W	3100	2700K	19"	14"	2-1/2"
CSF193100L30D1	35W	3100	3000K	19"	14"	2-1/2"



# CIRRUS

- White acrylic diffuser
- Option: battery back-up (add BB to end of model #)

## LED

- 120V TRIAC dimmable
- 50,000 hr. LED life, 90 CRI

White	LED	Source Lumens	CCT	DIA.	D
C2F091100L27D1	12W	1100	2700K	9"	3"
C2F091100L30D1	12W	1100	3000K	9"	3"
C2F111600L27D1	17W	1600	2700K	11"	3"
C2F111600L30D1	17W	1600	3000K	11"	3"
C2F142400L27D1	27W	2400	2700K	14"	3"
C2F142400L30D1	27W	2400	3000K	14"	3"
C2F193100L27D1	35W	3100	2700K	19"	3"
C2F193100L30D1	35W	3100	3000K	19"	3"





OUTDOOR



Textured Bronze



Textured Grey


# BLAINE

- Die-cast aluminum housing
- Durable powder coated finish
- White acrylic diffuser

## LED

- Minimum starting temp -20°F
- 120-277V universal-voltage driver
- 50,000 hr. LED life, 90 CRI

Textured Grey	Textured Bronze	LED	Source Lumens	CCT	H	W	D
BLW5161800L30MVTG	BLW5161800L30MVBZ	23W	1800	3000K	15-3/4"	4-3/4"	4-1/2"
BLW5232800L30MVTG	BLW5232800L30MVBZ	28W	2800	3000K	23"	4-3/4"	4-1/2"



OUTDOOR



Textured Grey



Textured Bronze


# BEAUMONT

- Die-cast aluminum housing
- Durable powder coated finish
- White acrylic diffuser

## LED

- Minimum starting temp -20°F
- 120-277V universal-voltage driver
- 50,000 hr. LED life, 90 CRI

Textured Grey	Textured Bronze	LED	Source Lumens	CCT	H	W	D
BMW5171800L30MVTG	BMW5171800L30MVBZ	19W	1800	3000K	14-3/4"	4-3/4"	4-3/8"
BMW5212800L30MVTG	BMW5212800L30MVBZ	24W	2800	3000K	21"	4-3/4"	4-1/2"



OUTDOOR



Textured Bronze



Textured Grey


# AVENUE

- Die-cast aluminum housing
- Durable powder coated finish
- White acrylic diffuser

## LED

- Minimum starting temp -20°F
- 120-277V universal-voltage driver
- 50,000 hr. LED life, 90 CRI

Textured Grey	Textured Bronze	LED	Source Lumens	CCT	H	W	D
AUW6122500L30MVTG	AUW6122500L30MVBZ	24W	2500	3000K	12"	5-1/2"	3-1/2"
AUW7183200L30MVTG	AUW7183200L30MVBZ	28W	3200	3000K	18"	7"	3-1/2"



OUTDOOR



Textured Grey





Textured Bronze


# LOGAN

- Die-cast aluminum housing
- Durable powder coated finish
- White acrylic diffuser

## LED

- Minimum starting temp -20°F
- 120-277V universal-voltage driver
- 50,000 hr. LED life, 90 CRI

Textured Grey	Textured Bronze	LED	Source Lumens	CCT	H	W	D
LGW6141800L30MVTG	LGW6141800L30MVBZ	16W	1800	3000K	14"	6-3/8"	4"



OUTDOOR



Textured Bronze



Textured Grey


# MAX

- Die-cast aluminum housing
- Durable powder coated finish
- White acrylic diffuser

## LED

- Minimum starting temp -20°F
- 120-277V universal-voltage driver
- 50,000 hr. LED life, 90 CRI

Textured Grey	Textured Bronze	LED	Source Lumens	CCT	H	W	D
MXW7122500L30MVTG	MXW7122500L30MVBZ	24W	2500	3000K	12"	7"	3-3/8"
MXW7183200L30MVTG	MXW7183200L30MVBZ	29W	3200	3000K	18"	7"	3-3/8"



OUTDOOR



Textured Bronze



Textured Grey


# STATE

- Die-cast aluminum housing
- Durable powder coated finish
- White acrylic diffuser

## LED

- Minimum starting temp -20°F
- 120-277V universal-voltage driver
- 50,000 hr. LED life, 90 CRI

Textured Grey	Textured Bronze	LED	Source Lumens	CCT	H	W	D
SEW5121500L30MVTG	SEW5121500L30MVBZ	19W	1500	3000K	12"	4-1/2"	3-1/2"
SEW5182300L30MVTG	SEW5182300L30MVBZ	24W	2300	3000K	17"	4-3/4"	3-1/2"



OUTDOOR



Satin Nickel



# BRIO

- Decorative metal bands
- White acrylic diffuser


## FLUORESCENT

- Photo sensor option (PC)
- Minimum starting temp 0°F
- 120V electronic ballast (EC)
- 120-277V universal-voltage ballast (MV)
- CFQ lamps (not included)

Satin Nickel	Oil-Rubbed Bronze	Qty.	Lamp	H	W	D
BRW218SNMV	BRW218RBMV	2	18W CFQ 4-Pin	18"	7-1/4"	4-5/8"
BRW218SNEC-PC	BRW218RBEC-PC	2	18W CFQ 4-Pin	18"	7-1/4"	4-5/8"



Oil-Rubbed Bronze







OUTDOOR



Satin Nickel

# ARIA MINI FLUSH

- Die-cast aluminum housing
- White glass diffuser

## LED

- Minimum starting temp -20°F
- 120V TRIAC dimmable driver
- 50,000 hr. LED life, 90 CRI



Oil-Rubbed Bronze

Satin Nickel	Oil-Rubbed Bronze	LED	Source Lumens	CCT	DIA.	H
ARMF07800L30D1SN	ARMF07800L30D1RB	8W	800	3000K	7"	3-5/8"



## Companion








# ARIA MINI

- Die-cast aluminum housing
- White glass diffuser

## LED

- Minimum starting temp -20°F
- 120V driver
- 50,000 hr. LED life, 90 CRI

Satin Nickel	LED	Source Lumens	CCT	H	W	D
ARW4800L30SN	11W	800	3000K	4-1/2"	4-7/8"	5-3/4"



Companion



OUTDOOR



Satin Nickel



# ARIA

- Die-cast aluminum housing
- Enclosed white glass diffuser


## FLUORESCENT

- Minimum starting temp 0°F
- 120V residential socket ballast
- CFQ lamp (not included)

Satin Nickel	Oil-Rubbed Bronze	Qty.	Lamp	H	W	D
ARW113SNEC*	ARW113RBEC*	1	13W CFQ 4-Pin	11"	4-3/8"	4"
ARW118SNEC	ARW118RBEC	1	18W CFQ 4-Pin	14-1/2"	5-3/8"	4-3/4"



Oil-Rubbed Bronze



## Companion





113

# CENTURY

- Die-cast metal accents
- White acrylic diffuser

## FLUORESCENT


- Photo sensor option (PC)
- Minimum starting temp 0°F
- 120V residential ballast
- CFQ lamp (not included)

Painted Nickel	Qty.	Lamp	H	W	D
CEW113PNEC	1	13W CFQ 4-Pin	10-1/8"	7-3/8"	4-5/8"
CEW113PNEC-PC	1	13W CFQ 4-Pin	10-1/8"	7-3/8"	4-5/8"
CEW118PNEC	1	18W CFQ 4-Pin	12-1/2"	7-3/8"	4-5/8"
CEW118PNEC-PC	1	18W CFQ 4-Pin	12-1/2"	7-3/8"	4-5/8"



118

OUTDOOR



Companion








# BILBAO

- Aluminum bands
- White acrylic diffuser

## FLUORESCENT

- Photo sensor option (PC)
- Minimum starting temp 0°F
- 120V residential ballast
- CFQ lamp (not included)

Satin Aluminum	Qty.	Lamp	H	W	D
BBW113SAEC	1	13W CFQ 4-Pin	9"	8"	4"
BBW113SAEC-PC	1	13W CFQ 4-Pin	9"	8"	4"



Companion



OUTDOOR




# BRONSON


- Die-cast aluminum housing
- Clear seeded glass diffuser

## LED

- Minimum starting temp -20°F
- 120V residential driver
- 50,000 hr. LED life, 80 CRI

Black	LED	Source Lumens	CCT	H	W	D
BNSW20045LBKCS	6W	240	4500K	13"	7-1/4"	8-1/2"






# HANOVER

- Die-cast aluminum housing
- Amber tinted glass diffuser

## LED

- Minimum starting temp -20°F
- 120V residential driver
- 50,000 hr. LED life, 80 CRI

Oil-Rubbed Bronze	LED	Source Lumens	CCT	H	W	D
HNSW20045LRSTS	8W	320	4500K	10"	6"	6-1/4"



OUTDOOR





113

# FUSION

- Die-cast metal ends
- White textured glass diffuser


## FLUORESCENT

- Photo sensor option (PC)
- Minimum starting temp 0°F
- 120V electronic ballast
- CFQ lamp(s) not included

Satin Nickel	Qty.	Lamp	H	W	D
FUW113SNEC	1	13W CFQ 4-Pin	9-1/2"	5-3/8"	4"
FUW113SNEC-PC	1	13W CFQ 4-Pin	9-1/2"	5-3/8"	4"
FUW213SNEC	2	13W CFQ 4-Pin	19"	5-3/8"	4"
FUW213SNEC-PC	2	13W CFQ 4-Pin	19"	5-3/8"	4"



213



Companion






# LED SECURITY

- Polycarbonate housing
- Frosted polycarbonate diffuser
- Integrated photocell for dusk-to-dawn operation

## LED

- Minimum starting temp -20°F
- 120V residential driver
- 50,000 hr. LED life, 80 CRI

Bronze	LED	Source Lumens	CCT	H	W	D
BWSW1600L41RB	18W	1620	4100K	10"	7-1/2"	4-3/8"




- Polycarbonate housing
- Frosted polycarbonate diffuser
- Integrated photocell for dusk-to-dawn operation

## LED

- Minimum starting temp -20°F
- 120V residential driver
- 50,000 hr. LED life, 80 CRI

Bronze	LED	Source Lumens	CCT	H	W	D
BWSW2400L41RB	27W	2430	4100K	11"	6-3/8"	5-1/2"



OUTDOOR


# LED FLOOD

- Die-cast aluminum housing
- Clear polycarbonate prismatic diffuser

## LED

- Minimum starting temp -20°F
- 120V residential driver
- 50,000 hr. LED life, 80 CRI

Black	LED	Source Lumens	CCT	H	W	D
TPDW70050LBK	10.5W	700	5000K	4"	8"	5-7/8"
TPDW110050LBK	17W	1100	5000K	4"	8"	5-7/8"
TPDW1300L50BK	13.5W	1300	5000K	4"	8"	5-7/8"
TPDW2600L50BK	28W	2600	5000K	4"	8"	5-7/8"




- Die-cast aluminum housing with back plate
- Clear polycarbonate prismatic diffuser
- Dusk-to-dawn operation with motion sensor

## LED

- Minimum starting temp -20°F
- 120V residential driver
- 50,000 hr. LED life, 80 CRI

Bronze	LED	Source Lumens	CCT	Sensor Range	H	W	D
TPDW1300L50RBMS	14W	1300	5000K	180°	8"	8"	6-1/2"
TPDW2600L50RBMS	29W	2600	5000K	240°	8"	8"	6-1/2"



OVERBED



Espresso/Jute

# HARVARD

- Solid wood accent detail
- LumaFuse™ laminated fabric/acrylic shade
- White acrylic bottom and top diffuser
- 4-way pull switch with night light


## LED

- 50,000 hr. LED life, 90 CRI



Weathered Grey/Linen White

Jute		Jute		LED	Source Lumens	CCT	L	H	D
Weathered Grey	Espresso	Weathered Grey	Espresso						
HVB384000L30ENWG-JT	HVB384000L30ENES-JT	56W	1350 up/2700 down	3000K	38"	4-7/8"	4"		
HVB505400L30ENWG-JT	HVB505400L30ENES-JT	68W	1800 up/3600 down	3000K	50"	4-7/8"	4"		
Linen White		Linen White		LED	Source Lumens	CCT	L	H	D
Weathered Grey	Espresso	Weathered Grey	Espresso						
HVB384000L30ENWG-LW	HVB384000L30ENES-LW	56W	1350 up/2700 down	3000K	38"	4-7/8"	4"		
HVB505400L30ENWG-LW	HVB505400L30ENES-LW	68W	1800 up/3600 down	3000K	50"	4-7/8"	4"		





Oil-Rubbed Bronze/Jute

# RANDOLPH

- Faux metal finish
- LumaFuse™ laminated fabric/acrylic shade
- White acrylic bottom and top diffuser
- 4-way pull switch with night light

## LED

- 50,000 hr. LED life, 90 CRI



Satin Nickel/Linen White

### Jute

**Satin Nickel**  
RAB384000L30ENSN-JT  
RAB505400L30ENSN-JT

### Jute

**Oil-Rubbed Bronze**  
RAB384000L30ENRB-JT  
RAB505400L30ENRB-JT

LED	Source Lumens	CCT	L	H	D
56W	1350 up/2700 down	3000K	38"	4-7/8"	4"
68W	1800 up/3600 down	3000K	50"	4-7/8"	4"


### Linen White

**Satin Nickel**  
RAB384000L30ENSN-LW  
RAB505400L30ENSN-LW


### Linen White

**Oil-Rubbed Bronze**  
RAB384000L30ENRB-LW  
RAB505400L30ENRB-LW

LED	Source Lumens	CCT	L	H	D
56W	1350 up/2700 down	3000K	38"	4-7/8"	4"
68W	1800 up/3600 down	3000K	50"	4-7/8"	4"



Espresso Weathered Grey



Jute Linen White

OVERBED



Weathered Grey/Jute

# CLAYTON

- Solid wood accent detail
- LumaFuse™ laminated fabric/acrylic shade
- White acrylic bottom and top diffuser
- 4-way pull switch with night light


## LED

- 50,000 hr. LED life, 90 CRI



Espresso/Linen White

Jute		Jute		LED	Source Lumens	CCT	L	H	D
Weathered Grey	Espresso	CYB384000L30ENWG-JT	CYB384000L30ENES-JT						
		56W	1350 up/2700 down	3000K	38"	5-1/4"	4"		
		68W	1800 up/3600 down	3000K	50"	5-1/4"	4"		
Linen White		Linen White		LED	Source Lumens	CCT	L	H	D
Weathered Grey	Espresso	CYB384000L30ENWG-LW	CYB384000L30ENES-LW						
		56W	1350 up/2700 down	3000K	38"	5-1/4"	4"		
		68W	1800 up/3600 down	3000K	50"	5-1/4"	4"		






Oil-Rubbed Bronze/Linen White

# SHEFFIELD

- Faux metal finish
- LumaFuse™ laminated fabric/acrylic shade
- White acrylic bottom and top diffuser
- 4-way pull switch with night light

## LED


- 50,000 hr. LED life, 90 CRI




Satin Nickel/Linen White

OVERBED

Jute		Jute		LED	Source Lumens	CCT	L	H	D
Satin Nickel		Oil-Rubbed Bronze							
SLB384000L30ENSN-JT	SLB384000L30ENRB-JT	SLB384000L30ENRB-JT	SLB384000L30ENRB-JT	56W	1350 up/2700 down	3000K	38"	4-3/8"	4"
SLB505400L30ENSN-JT	SLB505400L30ENRB-JT	SLB505400L30ENRB-LW	SLB505400L30ENRB-LW	68W	1800 up/3600 down	3000K	50"	4-3/8"	4"
Linen White		Linen White		LED	Source Lumens	CCT	L	H	D
Satin Nickel		Oil-Rubbed Bronze							
SLB384000L30ENSN-LW	SLB384000L30ENRB-LW	SLB384000L30ENRB-LW	SLB384000L30ENRB-LW	56W	1350 up/2700 down	3000K	38"	4-3/8"	4"
SLB505400L30ENSN-LW	SLB505400L30ENRB-LW	SLB505400L30ENRB-LW	SLB505400L30ENRB-LW	68W	1800 up/3600 down	3000K	50"	4-3/8"	4"





Oakley Bronze

# ALGIERS

- Metal trim ends
- Linen acrylic diffuser
- 4-way pull switch with night light

## LED

- 50,000 hr. LED life, 90 CRI



Satin Nickel

Satin Nickel		Oakley Bronze		LED	Source Lumens	CCT	L	H	D
ALB374000L30ENSN-LA	ALB374000L30ENKB-LA	56W	1350 up/2700 down	3000K	44-1/4"	4-5/8"	4"		
ALB495400L30ENSN-LA	ALB495400L30ENKB-LA	68W	1800 up/3600 down	3000K	56-1/4"	4-5/8"	4-7/8"		

## LED



## Companion







Satin Nickel

# SHERIDAN

- Decorative metal trim
- White linen patterned acrylic front diffuser
- White acrylic bottom and clear top diffuser
- 4-way pull switch with night light



Champagne

## LED

- 50,000 hr. LED life, 90 CRI

Satin Nickel	Champagne	LED	Source Lumens	CCT	L	H	D
SHB444000L30ENSN	SHB444000L30ENAC	56W	1350 up/2700 down	3000K	44-1/4"	4-5/8"	6-1/2"
SHB565400L30ENSN	SHB565400L30ENAC	68W	1800 up/3600 down	3000K	56-1/4"	4-5/8"	6-1/2"



## FLUORESCENT

- 120V electronic ballast
- 120-277V universal-voltage option available without switch and nightlight (consult factory)
- Lamps not included

Satin Nickel	Champagne	Qty.	Lamp	L	H	D
SHB325SNE8-LA	SHB325ACE8-LA	3	F25T8	44-1/4"	4-5/8"	6-1/2"
SHB332SNE8-LA	SHB332ACE8-LA	3	F32T8	56-1/4"	4-5/8"	6-1/2"



OVERBED




Brushed Nickel

### Overbed Lighting Functions



All On



Downlight



Uplight



Mahogany

# IDEAL

- Tapered front with faux wood finish accents
- White acrylic diffuser
- 4-way pull switch with night light

## LED

- 50,000 hr. LED life, 90 CRI

Brushed Nickel	Light Oak	Mahogany	LED	Source Lumens	CCT	L	H	D
IDB394000L30ENBN	IDB394000L30ENLK	IDB394000L30ENMH	56W	1350 up/2700 down	3000K	39-15/16"	5-3/8"	6-1/4"
IDB515400L30ENBN	IDB515400L30ENLK	IDB515400L30ENMH	68W	1800 up/3600 down	3000K	51-15/16"	5-3/8"	6-1/4"



## FLUORESCENT

- 120V electronic ballast
- 120-277V universal-voltage option available without switch and night light (consult factory)
- Lamps not included

Brushed Nickel	Light Oak	Mahogany	Qty.	Lamp	L	H	D
IDB325E8BN	IDB325E8LK	IDB325E8MH	3	F25T8	39-15/16"	5-3/8"	6-1/4"
IDB332E8BN	IDB332E8LK	IDB332E8MH	3	F32T8	51-15/16"	5-3/8"	6-1/4"



Light Oak

Companion





Taupe

# HINSDALE

- Solid wood crown molding frame
- White acrylic bottom and clear top diffuser
- 4-way pull switch with night light

## LED

- 50,000 hr. LED life, 90 CRI



Ivory	Taupe	White	LED	Source Lumens	CCT	L	H	D
HDB434000L30ENPI	HDB434000L30ENTT	HDB434000L30ENWH	56W	1350 up/2700 down	3000K	43"	6"	7-1/4"
HDB555400L30ENPI	HDB555400L30ENTT	HDB555400L30ENWH	68W	1800 up/3600 down	3000K	55"	6"	7-1/4"



## FLUORESCENT

- 120V electronic ballast
- 120-277V universal-voltage option available without switch and night light (consult factory)
- Lamps not included

Ivory	Taupe	White	Qty.	Lamp	L	H	D
HDB325PIE8	HDB325TTE8	HDB325WHE8	3	F25T8	43"	6"	7-1/4"
HDB332PIE8	HDB332TTE8	HDB332WHE8	3	F32T8	55"	6"	7-1/4"





Espresso

# CAMERON

- Solid wood trim frame
- White acrylic bottom and clear top diffuser
- 4-way pull switch with night light

## LED

- 50,000 hr. LED life, 90 CRI



Cherry

Cherry	Espresso	LED	Source Lumens	CCT	L	H	D
CMB394000L30ENCH	CMB394000L30ENES	56W	1350 up/2700 down	3000K	39-5/8"	6"	5-3/4"
CMB515400L30ENCH	CMB515400L30ENES	68W	1800 up/3600 down	3000K	51-5/8"	6"	5-3/4"



## FLUORESCENT

- 120V electronic ballast
- 120-277V universal-voltage option available without switch and night light (consult factory)
- Lamps not included

Cherry	Espresso	Qty.	Lamp	L	H	D
CMB325CHE8	CMB325ESE8	3	F25T8	39-5/8"	6"	5-3/4"
CMB332CHE8	CMB332ESE8	3	F32T8	51-5/8"	6"	5-3/4"



OVERBED



# BILBAO

- Linear aluminum accent bands
- White acrylic front, bottom and top diffuser
- 4-way pull switch with night light

## LED

- 50,000 hr. LED life, 90 CRI

Satin Aluminum	LED	Source Lumens	CCT	L	H	D
BBB434000L30ENSA	56W	1350 up/2700 down	3000K	43"	5-1/4"	5-5/8"
BBB555400L30ENSA	68W	1800 up/3600 down	3000K	55"	5-1/4"	5-5/8"



## FLUORESCENT

- 120V electronic ballast
- 120-277V universal-voltage option available without switch and night light (consult factory)
- Lamps not included

Satin Aluminum	Qty.	Lamp	L	H	D
BBB325SAE8	3	F25T8	43"	5-1/4"	5-5/8"
BBB332SAE8	3	F32T8	55"	5-1/4"	5-5/8"



Companion





OVERBED



# PALMETTO

- Off white alabaster acrylic diffuser
- White acrylic bottom and top diffuser
- 4-way pull switch with night light

## LED

- 50,000 hr. LED life, 90 CRI

Alabaster	LED	Source Lumens	CCT	L	H	D
PLB424000L30EN	56W	1350 up/2700 down	3000K	42-1/2"	5-1/4"	5-1/8"
PLB545400L30EN	68W	1800 up/3600 down	3000K	54-1/4"	5-1/4"	5-1/8"

## LED

## FLUORESCENT

- 120V electronic ballast
- 120-277V universal-voltage option available without switch and night light (consult factory)
- Lamps not included

Alabaster	Qty.	Lamp	L	H	D
PLB325ALE8	3	F25T8	42-1/4"	5-1/4"	5-1/8"
PLB332ALE8	3	F32T8	54-1/4"	5-1/4"	5-1/8"

## FL





# DECORATIVE LINEAR



White

# ZURICH

- LED flat panel, low profile construction
- Extruded metal frame


## LED

- 120V TRIAC dimmable
- 50,000 hr. LED life, 90 CRI



Satin Nickel  
1 ft. x 2 ft.

		LED	Source Lumens	CCT	L	W	H
<b>Satin Nickel</b>	<b>White</b>						
ZUF12241800L30D1SN	ZUF12241800L30D1WH	26W	1800	3000K	27"	15"	2-3/8"
ZUL12483200L30D1SN	ZUL12483200L30D1WH	39W	3200	3000K	51"	15"	2-3/8"



Companion





White

# SLOANE

- LED flat panel, low profile construction
- Extruded metal frame


## LED

- 120V TRIAC dimmable
- 50,000 hr. LED life, 90 CRI



Satin Nickel

		Source			L	W	H
		LED	Lumens	CCT			
Satin Nickel	SLF12241800L30D1SN	26W	1800	3000K	27"	15"	2"
	SLL12483200L30D1SN	39W	3200	3000K	50-1/4"	15"	2"
White	SLF12241800L30D1WH	26W	1800	3000K	27"	15"	2"
	SLL12483200L30D1WH	39W	3200	3000K	50-1/4"	15"	2"



Companion






Satin Nickel

# ATLAS

- LED flat panel, low profile construction
- Extruded metal frame


## LED

- 120V TRIAC dimmable
- 50,000 hr. LED life, 90 CRI



Oil-Rubbed Bronze

Satin Nickel		Oil-Rubbed Bronze		LED	Source Lumens	CCT	L	W	H
ATLF12241800L30D1SN	ATLF12241800L30D1RB	26W	1800	3000K	26-3/4"	15"	2"		
ATL12483200L30D1SN	ATL12483200L30D1RB	39W	3200	3000K	50-3/8"	15"	2"		



Companion





Satin Nickel

# HIGHLAND

- Perforated metal design
- White acrylic inner diffuser
- Adjustable hanging cable up to 48" included
- Without cable kit (NN,WN models)
- Optional stem mount kits available

## FLUORESCENT

- 120-277V universal-voltage ballast
- Lamps not included

Nickel	White	Qty.	Lamp	L	W	H
HPL332NMV	HPL332WMV	3	F32T8	49-3/4"	11"	4-1/4"
HPL332NNMV	HPL332WNMV	3	F32T8	49-3/4"	11"	4-1/4"



White

DECORATIVE LINEAR

HKR	HKS	HKC

\*Stems - White (Ordered Separately)

Rigid	Swivel	Length
HKR18W	HKS18W	18"
HKR24W	HKS24W	24"
HKR30W	HKS30W	30"

Cable Kit	Length
HKC	48"

**Joiner**  
HPLJN-Nickel  
HPLJW-White

\*Stems are listed as individual units  
order in pairs to increase height





Satin Aluminum



Oil-Rubbed Bronze

## AEON SUSPENDED

- Satin aluminum with white acrylic diffuser
- Oil-rubbed bronze with linen acrylic diffuser
- Direct/Indirect light output
- 12" stem kit or 45" cable kit (CK)

### FLUORESCENT

- 120-277V universal-voltage ballast
- Lamps not included


Satin Aluminum	Oil-Rubbed Bronze	Qty.	Lamp	L	W	H
AEL232SAMV	AEL232RBMV	2	F32T8	53-3/8"	16"	17-3/8"
AEL432SAMV	AEL432RBMV	4	F32T8	53-3/8"	22"	17-3/8"
AEL232SAMV-CK	AEL232RBMV-CK	2	F32T8	53-3/8"	16"	ADJ.
AEL432SAMV-CK	AEL432RBMV-CK	4	F32T8	53-3/8"	22"	ADJ.

### Stems/Cable Kit (Ordered Separately)

Satin Aluminum	
STEM-SA-06	6" Stem
STEM-SA-12	12" Stem
STEM-SA-24	24" Stem
CK4W-SA	45" Cable Kit w/Canopy

Oil-Rubbed Bronze	
STEM-RB-06	6" Stem
STEM-RB-12	12" Stem
STEM-RB-24	24" Stem
CK4W-RB	45" Cable Kit w/Canopy

\*Stems are listed as individual units-order in pairs to increase height





Satin Aluminum



Oil-Rubbed Bronze

# AEON

- Satin aluminum with white acrylic diffuser
- Oil-rubbed bronze with linen acrylic diffuser

## LED

- 50,000 hr. LED life, available in 3000 lumens (28W) or 5000 lumens (46W), 90 CRI

53-3/8" L x 16" W x 4-3/8" H  
53-3/8" L x 22" W x 4-3/8" H

Series	Size (Inches)		LED	CCT	Driver	Finish
	W	Source Lumens				
AELF	16	= 3000	L	27 2700K	D1 Voltage (120V TRIAC Dimming) D2 Voltage (120-277V 0-10V Dimming)	RB Oil-Rubbed Bronze SA Satin Aluminum
	22	= 5000		30 3000K		

Example: AELF163000L30D1SA



## FLUORESCENT

- 120-277V universal-voltage ballast
- Lamps not included

Satin Aluminum	Oil-Rubbed Bronze	Qty.	Lamp	L	W	H
AELF232SAMV	AELF232RBMV	2	F32T8	53-3/8"	16"	4-3/8"
AELF432SAMV	AELF432RBMV	4	F32T8	53-3/8"	22"	4-3/8"





Satin Nickel



Oil-Rubbed Bronze

# GIZELLE

- Tapered low profile
- White acrylic diffuser


## FLUORESCENT

- 120V electronic ballast (R8)
- 120-277V universal-voltage ballast (MV)
- Lamps not included

Satin Nickel	Oil-Rubbed Bronze	Qty.	Lamp	L	W	H
GZL432SNR8	GZL432RBR8	4	F32T8	48-3/8"	17"	3-5/8"
GZL432SNMV	GZL432RBMV	4	F32T8	48-3/8"	17"	3-5/8"



Maple



Cherry


# MISSION

- Solid wood molding
- White acrylic diffuser

## FLUORESCENT

- 120V electronic ballast
- Lamps not included

Cherry	Maple	Qty.	Lamp	L	W	H
MCC232R8	MCM232R8	2	F32T8	49-1/2"	11-1/4"	3-1/2"
MCC2U3R8	MCM2U3R8	2	FB32T8	25-1/4"	25-1/4"	3-1/2"
MCC432R8	MCM432R8	4	F32T8	49-1/2"	17-1/4"	3-1/2"







# WINCHESTER

- Solid wood crown molding
- White acrylic diffuser

## FLUORESCENT

- 120V electronic ballast (R8)
- 120-277V universal-voltage ballast (MV)
- Lamps not included

Cherry	Oak	Unfinished Oak	White	Qty.	Lamp	L	W	H
CCM232R8	KCM232R8	UCM232R8	WCM232R8	2	F32T8	51-3/8"	13-1/2"	3-3/8"
CCM2U3R8	KCM2U3R8	UCM2U3R8	WCM2U3R8	2	FB32T8	27-3/4"	27-3/4"	3-3/8"
CCM432R8	KCM432R8	UCM432R8	WCM432R8	4	F32T8	51-3/8"	18-1/4"	3-3/8"
CCM232MV	KCM232MV	UCM232MV	WCM232MV	2	F32T8	51-3/8"	13-1/2"	3-3/8"
CCM2U3MV	KCM2U3MV	UCM2U3MV	WCM2U3MV	2	FB32T8	27-3/4"	27-3/4"	3-3/8"
CCM432MV	KCM432MV	UCM432MV	WCM432MV	4	F32T8	51-3/8"	18-1/4"	3-3/8"



# CONROE

- Half round wood mold
- White acrylic diffuser

## FLUORESCENT

- 120V electronic ballast
- 120-277V universal-voltage ballast
- Lamps not included

### Satin Nickel

120V	120-277V	Qty.	Lamp	L	W	H
CN232R8	CN232MV	2	F32T8	50"	12-1/2"	3-1/2"
CN2U3R8	CN2U3MV	2	FB32T8	25-7/8"	25-7/8"	3-1/2"
CN432R8	CN432MV	4	F32T8	50"	17-5/8"	3-1/2"



DECORATIVE LINEAR



# LED CLOUD

- Narrow profile
- White acrylic diffuser

## LED

- 120V TRIAC dimmable
- 50,000 hr. LED life, 90 CRI

Warm White	LED	Source Lumens	CCT	L	W	H
LCL3000L30D1	36W	3000	3000K	49-3/4"	9-3/8"	3-1/4"
LCL4100L30D1	52W	4100	3000K	49-3/4"	9-3/8"	3-1/4"
LCL5000L30D1	60W	5000	3000K	49-3/4"	9-3/8"	3-1/4"

Cool White	LED	Source Lumens	CCT	L	W	H
LCL3000L40D1	36W	3000	4000K	49-3/4"	9-3/8"	3-1/4"
LCL4100L40D1	52W	4100	4000K	49-3/4"	9-3/8"	3-1/4"
LCL5000L40D1	60W	5000	4000K	49-3/4"	9-3/8"	3-1/4"



# COURTLAND

- Low profile
- White acrylic diffuser

## FLUORESCENT

- 120V electronic ballast (R8)
- 120-277V universal-voltage ballast (MV)
- Lamps not included

White	Qty.	Lamp	L	W	H
CLL232R8	2	F32T8	52"	11-1/2"	3-3/4"
CLL232MV	2	F32T8	52"	11-1/2"	3-3/4"
CLL428MV	4	F28T5	52"	11-1/2"	3-3/4"





# LARGO

- Full size profile
- White acrylic diffuser
- Lift and shift mount
- Order diffuser and housing separately

## FLUORESCENT

- 120-277V universal-voltage ballast
- Lamps not included

White Diffuser	White Housing	Qty.	Lamp	L	W	H
RC14	CSW142MV	2	F32T8	51-3/4"	15"	6"
RC14	CSW144MV	4	F32T8	51-3/8"	15"	6"
RC22	CSW224MV	4	F17T8	27-1/2"	27"	6"
RC22	CSW2U4MV	2	FB32T8	27-1/2"	27"	6"
RC24	CSW244MV	4	F32T8	51-1/2"	27"	6"



# RIGBY

- Narrow profile
- White acrylic diffuser
- Lift and shift mount

## FLUORESCENT

- 120V electronic ballast (R8)
- 120-277V universal-voltage ballast (MV)
- Lamps not included

White	120-277V	Qty.	Lamp	L	W	H
RC232R8	RC232MV	2	F32T8	50-3/4"	10-1/2"	4-7/8"
RC2U3R8	RC2U3MV	2	FB32T8	27-1/2"	27"	6"
RC417R8	RC417MV	4	F17T8	24-1/2"	15"	5-1/4"
RC432R8	RC432MV	4	F32T8	50-3/4"	15"	5-1/4"



# MARINA

- Narrow square cloud
- White acrylic diffuser
- Lift and shift mount



## FLUORESCENT

- 120V electronic ballast (R8)
- 120-277V universal-voltage ballast (MV)
- Lamps not included

White	Qty.	Lamp	L	W	H
MAR232R8	2	F32T8	50"	9-3/4"	3-5/8"
MAR232MV	2	F32T8	50"	9-3/4"	3-5/8"
MAR432R8	4	F32T8	50"	16-1/4"	3-5/8"
MAR432MV	4	F32T8	50"	16-1/4"	3-5/8"



# MALIBU

- Full size square profile
- White acrylic diffuser
- Lift and shift mount
- Order diffuser and housing separately



## FLUORESCENT

- 120-277V universal-voltage ballast
- Lamps not included

White Diffuser	Housing	Qty.	Lamp	L	W	H
MAR14	CSW142MV	2	F32T8	50"	14"	5"
MAR14	CSW144MV	4	F32T8	50"	14"	5"
MAR22	CSW224MV	4	F17T8	25-1/2"	26"	5"
MAR22	CSW2U4MV	2	FB32T8	25-1/2"	26"	5"
MAR24	CSW244MV	4	F32T8	50"	26"	5"



# LED WRAP




- White steel housing
- Frosted white prismatic acrylic diffuser

## LED

- 120V TRIAC dimmable (D1)
- 120-277V, 0-10V DC dimmable (D2)
- 50,000 hr. LED life, 90 CRI
- \*DLC Listed only - 3000K, 80 CRI

Warm White				LED	Source Lumens	CCT	L	W	H	Cool White			
*LWL07242500L30D1	30W	2500	3000K	24"	7"	2-3/8"	*LWL07242500L40D1	30W	2500	3000K	24"	7"	2-3/8"
*LWL07483000L30D1	36W	3000	3000K	48"	7"	2-3/8"	*LWL07483000L40D1	36W	3000	4000K	48"	7"	2-3/8"
*LWL07485000L30D1	60W	5000	3000K	48"	7"	2-3/8"	*LWL07485000L40D1	60W	5000	4000K	48"	7"	2-3/8"
*LWL07242500L30D2	30W	2500	3000K	24"	7"	2-3/8"	*LWL07242500L40D2	30W	2500	3000K	24"	7"	2-3/8"
*LWL07483000L30D2	36W	3000	3000K	48"	7"	2-3/8"	*LWL07483000L40D2	36W	3000	4000K	48"	7"	2-3/8"
*LWL07485000L30D2	60W	5000	3000K	48"	7"	2-3/8"	*LWL07485000L40D2	60W	5000	4000K	48"	7"	2-3/8"



Prismatic



White

# NARROW WRAP

- White steel housing
- Clear prismatic or white acrylic diffuser
- Flush, stem or row mounting

## FLUORESCENT

- 120V electronic ballast
- 120-277V universal-voltage ballast
- Lamps not included

Prismatic		120V		120-277V		Qty.	Lamp	L	W	H
LW217R8	LW217AMV	2	F17T8	24"	7"	2-3/8"				
LW232R8	LW232AMV	2	F32T8	48"	7"	2-3/8"				
LW432R8	LW432AMV	4	F32T8	48"	11-1/2"	2-3/8"				

White		120V		120-277V		Qty.	Lamp	L	W	H
LW217WAR8	LW217WAMV	2	F17T8	24"	7"	2-3/8"				
LW232WAR8	LW232WAMV	2	F32T8	48"	7"	2-3/8"				
LW432WAR8	LW432WAMV	4	F32T8	48"	11-1/2"	2-3/8"				





# LED STRIPLIGHT

- Pre-finished white steel housing
- White acrylic diffuser

## LED

- 120-277V universal-voltage driver
- 50,000 hr. LED life, 90 CRI

Cool White	LED	Source Lumens	CCT	L	W	H
LSL484100L40MVWH	34W	4100	4000K	48"	5"	3-5/16"



# STANDARD STRIPLIGHT

- Pre-finished white steel housing
- Flush, stem or row mounting

## FLUORESCENT

- 120V electronic ballast
- 120-277V universal-voltage ballast
- Lamp(s) not included

### Single

120V	120-277V	Qty.	Lamp	L	W	H
ST115R8		1	F15T8	18"	3-1/8"	3-1/4"
ST117R8	ST117MV	1	F17T8	24"	3-1/8"	3-1/4"
ST125R8	ST125MV	1	F25T8	36"	3-1/8"	3-1/4"
ST132R8	ST132MV	1	F32T8	48"	3-1/8"	3-1/4"

### Double

120V	120-277V	Qty.	Lamp	L	W	H
ST217R8	ST217MV	2	F17T8	24"	4-3/4"	3-3/4"
ST225R8	ST225MV	2	F25T8	36"	4-3/4"	3-3/4"
ST232R8	ST232MV	2	F32T8	48"	4-3/4"	3-3/4"
	ST232-8MV	4	F32T8	96"	4-3/4"	3-3/4"





# COMMERCIAL GRADE STRIPLIGHT

- Pre-finished white steel housing
- Flush, stem or row mounting

## FLUORESCENT

- 120-277V universal-voltage ballast
- Lamps not included

### 430 mA Slimline

120-277V	Qty.	Lamp	L	W	H
S296MV	2	F96T8	96"	4-1/4"	3-3/4"



# LOW-PROFILE STRIPLIGHT

- Pre-finished white steel housing
- Flush, stem or row mounting

## FLUORESCENT

- 120-277V universal-voltage ballast
- Energy efficient T5 technology
- Lamp(s) not included

Single	Qty.	Lamp	L	W	H
STN114MV	1	F14T5	22-3/8"	1-7/8"	2-3/8"
STN121MV	1	F21T5	34-3/8"	1-7/8"	2-3/8"
STN128MV	1	F28T5	46-3/8"	1-7/8"	2-3/8"

Double	Qty.	Lamp	L	W	H
STN214MV	2	F14T5	22-3/4"	3-1/8"	2-3/8"
STN221MV	2	F21T5	34-3/4"	3-1/8"	2-3/8"
STN228MV	2	F28T5	46-3/4"	3-1/8"	2-3/8"





# LED VAPORTITE

- Impact resistant white polycarbonate housing
- Clear polycarbonate diffuser
- Continuous gasket offers secure seal against dust and moisture
- Includes mounting brackets and water tight connector

## LED

- 120-277V universal-voltage driver
- 50,000 hr. LED life, 90 CRI

Cool White	LED	Source Lumens	CCT	L	W	H
VTL483500L40MV	34W	3500	4000K	48"	6-3/4"	5-1/8"



# VAPORTITE

- Reinforced fiberglass housing
- Spring mounted easy install diffuser brackets
- Molded, high impact acrylic
- Continuous gasket offers secure seal against dust and moisture
- Includes mounting brackets and water tight connector

## FLUORESCENT

- 120-277V universal-voltage ballast
- Lamps not included

White	Qty.	Lamp	L	W	H
VTL228MV	2	F28T5	50"	6-3/4"	5-1/8"
VTL232MV	2	F32T8	50"	6-3/4"	5-1/8"
VTL228-8MV	4	F28T5	98"	6-3/4"	5-1/8"
VTL232-8MV	4	F32T8	98"	6-3/4"	5-1/8"





# UNDERCABINET



## SLATE™ PRO

Color-Control LED Panel System

### Brightness and color, both at your command

For new construction or renovation, the Slate Pro Color-Control LED system provides unprecedented flexibility to tailor under-cabinet lighting to suit the setting, facilitate a task, or help set a mood. In addition to the superior optics of edge-lit LED technology, Slate features an innovative 3-function control.



Slate's dual adjustment has been designed to give control over lighting the kitchen environment. While preparing food for dinner guests, a full brightness may be preferred, with color temperature set to a cool and clean visibility level. When company arrives, a more sociable mood can be created by bringing the dimmer down and adjusting to a warm setting.



FULL RANGE  
WARM-TO-COOL  
COLOR CONTROL



FULL RANGE  
DIMMING CONTROL



UNDERCABINET



4000°K  
Cool Daylight



2700°K  
Warm White

# SLATE™ PRO

## Color-Control LED Panel System

- One-touch full-range dimming
- One-touch color temperature (CCT) adjustment, from warm to cool (2700°K-4000°K)
- Edge-Lit LED panels provide evenly distributed, glare-free light for all surfaces
- Linkable panels includes multiple connectors for a variety of layout options
- Ultra-low 1/2" LED panel profile
- Dual-run capability allows full installation flexibility
- 500 lumens per foot, 90 CRI
- Title 24 compliant
- Powder-coated housing with molded end caps
- Each panel includes 12" connecting cable and direct connector
- Easy, flexible DC installation
- 120VAC input, 36W - 144W DC (Depending on Power Supply)
- 2 power supply options (36W and 72W)
- Optional occupancy sensor (motion), page 245
- Patent Pending



### LED Panels

Size	White	Oil-Rubbed Bronze	Lumens Watts	4000K	LPW	L	W	D
9 in.	SPLE9WH	SPLE9RB	4.5W	375	58	9"	5"	1/2"
14 in.	SPLE14WH	SPLE14RB	7.5W	585	60	14"	5"	1/2"
22 in.	SPLE22WH	SPLE22RB	12W	920	60	22"	5"	1/2"
32 in.	SPLE32WH	SPLE32RB	18W	1330	60	32"	5"	1/2"
40 in.	SPLE40WH	SPLE40RB	22W	1670	60	40"	5"	1/2"

Each panel includes (1) one:  
 - 12" interconnect cord  
 - Direct connector

### Control Switch (required)


LCX-CON	Watts	L	W	D
	144 Max.	2-7/8"	1-3/4"	1/2"



Each switch includes (1) one:  
 - J-box mounting bracket  
 - Alternative under cabinet cover plate  
 - DC interconnect cable (8' long)

### Power Supply (required)

LCX-PWR36	LCX-PWR72	Watts	L	W	D
		36W	7-1/2"	2-1/2"	1-1/8"
		72W	7-1/2"	2-1/2"	1-1/8"



Each power supply includes (1) one:  
 - AC power cord  
 - DC input cord (10' long)

### Accessories

SPLECL24	24" Interconnect cord
SPLECL36	36" Interconnect cord
SPLECL48	48" Interconnect cord
SPLECL72	72" Interconnect cord



SPLEDC	Direct Connector
--------	------------------








## Versatile in-wall or under cabinet installation

The Slate Pro control can be easily installed in-wall, or surface-mounted for full installation flexibility.

The versatile power supply can be hard-wired or plugged into any standard 110v outlet.

IN-WALL CONTROL INSTALLATION



## Easy to specify, Easy to install

Each Slate Control can accommodate two power supplies and two panel runs. Just add the panel wattage to determine the Power Supply required.

panel size	panel watts	qty	total watts
14"	7.5	2	<b>15</b>
22"	12	3	<b>36</b>
32"	18	1	<b>18</b>
<b>total</b>			<b>69 watts</b>
Power supplies required:			(1) <b>72W</b>
Control (up to 144W total)			


# LED NOBLE PRO

- Plug-in or direct wire
- Linkable up to 200 watts with 12" connecting cable or direct wire
- Selectable switch - choose 1 of 3 color temperature levels: 2700K, 3000K or 4000K
- Dimmable with TRIAC wall dimmer, page 245
- White polycarbonate diffuser hides LEDs
- Fully integrated LEDs
- Title 24 compliant
- ≥ 90 CRI
- 50,000 hour LED life
- Hi-Low switch
- Rear access plate for quick wire connections
- Captive mounting screws
- Includes: connecting cable, cord & plug, direct connector & hardwire connector
- Extruded aluminum construction
- Additional accessories and optional occupancy sensor (motion), page 245



Size	White	Oil-Rubbed Bronze	Brushed Aluminum	Type	Lumens			LPW	L	W	D
					2.7K	3.0K	4.0K				
9 in.	NLLP9WH	NLLP9RB	NLLP9BA	4.6W SMT-Array	259	290	384	63	9"	3-3/4"	1"
14 in.	NLLP14WH	NLLP14RB	NLLP14BA	6.7W SMT-Array	384	437	442	65	14"	3-3/4"	1"
22 in.	NLLP22WH	NLLP22RB	NLLP22BA	10.7W SMT-Array	656	746	755	69	22"	3-3/4"	1"
32 in.	NLLP32WH	NLLP32RB	NLLP32BA	14.4W SMT-Array	927	1022	1023	70	32"	3-3/4"	1"
40 in.	NLLP40WH	NLLP40RB	NLLP40BA	18W SMT-Array	1170	1302	1310	72	40"	3-3/4"	1"

LPW based on 3000K color temperature



## Accessories



Order separately, see page 245




UNDERCABINET

# LED T5L



- Direct wire
- Hardwire only
- 3000K color temperature
- Dimmable with TRIAC wall dimmer, page 245
- White polycarbonate diffuser hides LEDs
- Fully integrated LEDs
- $\geq 80$  CRI
- 50,000 hour LED life
- On/off switch
- Multiple knockouts conveniently located
- Includes hardwire connector
- Stamped steel construction
- Optional occupancy sensor (motion), page 245

Size	White	Oil-Rubbed Bronze	Type	Lumens	LPW	L	W	D
12 in.	T5L12RWH	T5L12RRB	5W SMT-Array	315	63	12"	3-1/2"	1-1/8"
18 in.	T5L18RWH	T5L18RRB	7.5W SMT-Array	520	69	18"	3-1/2"	1-1/8"
21 in.	T5L21RWH	T5L21RRB	8.5W SMT-Array	570	67	21"	3-1/2"	1-1/8"
24 in.	T5L24RWH	T5L24RRB	9W SMT-Array	630	70	24"	3-1/2"	1-1/8"
33 in.	T5L33RWH	T5L33RRB	13.5W SMT-Array	950	70	33"	3-1/2"	1-1/8"
42 in.	T5L42RWH	T5L42RRB	16.5W SMT-Array	1150	69	42"	3-1/2"	1-1/8"




### Accessories





# XENON NXL


- Plug-in or direct wire
- Linkable with 12" connecting cable or direct connect up to 560 watts
- 5,000 hour, 20 watt bi-pin lamps included (2700K)
- Dimmable with standard 600 watt wall dimmer
- Tempered frosted glass diffuser
- Multiple back and top knockouts
- Push-in wire connectors for easy wiring
- Includes: connecting cable, cord & plug, direct connector & hardwire connector
- Captive mounting screws
- Sturdy steel construction
- Additional accessories and optional occupancy sensor (motion), page 245



Linkable!

Size	White	Bronze	Stainless	Type 120V	L	W	D
8 in.	NXL120WH	NXL120RB	NXL120SS	(1) 20W Xenon Bi-Pin	8"	3-3/4"	1"
14 in.	NXL220WH	NXL220RB	NXL220SS	(2) 20W Xenon Bi-Pin	14"	3-3/4"	1"
22 in.	NXL320WH	NXL320RB	NXL320SS	(3) 20W Xenon Bi-Pin	22"	3-3/4"	1"
32 in.	NXL420WH	NXL420RB	NXL420SS	(4) 20W Xenon Bi-Pin	32"	3-3/4"	1"
40 in.	NXL520WH	NXL520RB	NXL520SS	(5) 20W Xenon Bi-Pin	40"	3-3/4"	1"

**DIM**



## Accessories

<b>Included</b>					<b>Additional</b>			24", 36", 48", 60", 72" Connecting Cable Available in White or Black
	Power Cord	12" Connecting Cable	Connector	Hardwire Connector		Set of 4 Clips	Hardwire Box	

Order separately, see page 245

# T5 FLUORESCENT

- Direct wire
- White metal housing
- White diffuser snaps in and out for easy maintenance
- Multi-purpose hardwire fitting included
- 120V electronic ballast
- T5 lamp(s) required
- Also available with on/off switch and T5 lamps included (RT models, 4100K)



Standard	Lamps & Switch	Qty.	Lamp	L	W	D
T5U108	T5U108RT	1	F8T5	12-3/8"	3-5/8"	1-1/4"
T5U113	T5U113RT	1	F13T5	21-3/8"	3-5/8"	1-1/4"
T5U208	T5U208RT	2	F8T5	24-3/8"	3-5/8"	1-1/4"
T5U138	T5U138RT	2	(1) F13T5 & (1) F8T5	34-3/8"	3-5/8"	1-1/4"
T5U213	T5U213RT	2	F13T5	42-3/8"	3-5/8"	1-1/4"



## Accessories

Included



Hardwire Connector



# T8 FLUORESCENT

- Direct wire
- White metal housing
- White diffuser snaps in and out for easy maintenance
- Multi-purpose hardwire fitting included (excludes closet models)
- 120V electronic ballast
- T8 lamp(s) required
- Also available with on/off switch and convenience outlet (RCO models)
- 15W T8 lamp included (T models, 4100K)



Standard	Switch & Outlet	Pre-heat	Lamp & Switch	Qty.	Lamp	L	W	D
T8U15		T8U15PH	T8U15PHRT	1	F15T8	18"	4"	1-3/8"
T8U17	T8U17RCO			1	F17T8	24"	4"	1-3/8"
T8U25	T8U25RCO			1	F25T8	36"	4"	1-3/8"
T8U32	T8U32RCO			1	F32T8	48"	4"	1-3/8"

Pre-heat Closet	Qty.	Lamp	L	W	D
T8U15PHCLT	1	F15T8	18"	4"	1-3/8"
T8U15PHCLT-PS	1	F15T8	18"	4"	1-3/8"



## Accessories

Included



Hardwire Connector



- Closet light has special knockout pattern for universal J-box mounting
- Meets national electrical codes for closet lighting
- Available with pull-chain switch (PS)
- 15W T8 lamps included (4100K)

## Additional Accessories Noble Pro/NXL Series

### White Model #s

- XLCP60WH
  - 60" Cord & Plug
- XLHBWH
  - Hardwire Box
- XLCC24WH
  - 24" Interconnect Cord
- XLCC36WH
  - 36" Interconnect Cord
- XLCC48WH
  - 48" Interconnect Cord
- XLCC72WH
  - 72" Interconnect Cord

### Black Model #s

- XLCP60BL
  - 60" Cord & Plug
- XLHBBL
  - Hardwire Box
- XLCC24BL
  - 24" Interconnect Cord
- XLCC36BL
  - 36" Interconnect Cord
- XLCC48BL
  - 48" Interconnect Cord
- XLCC72BL
  - 72" Interconnect Cord

### Model # XLC-Clip

- Clear cord clip with screws (4 pieces)

## Occupancy Sensor (Motion) for Slate Pro/Nobel Pro/T5L

### Model # LCX-OCC

- Microwave sensor unit, on/off rocker switch
- Includes connecting cables that operate with Noble Pro (NLLP), xenon (NXL)
- Hardwire for T5L and Slate Pro (SPLE)

## Compatible Dimmers for Noble Pro/T5L

Brand	Model #
Cooper	6013W
Leviton	6633, 6681, 6621-WWP, 6631-WWP, DSE06-10Z
Lutron®	TG-600P, TG-603P, AY600P, MACL153MH, SELV-300P
Legrand®	T600WV, WS700TCCCVG



UNDERCABINET



# Hera®

## Light Years Ahead.

AFX Partner

Hera designs, develops and manufactures high-quality lighting solutions specifically for cabinets, furniture and displays. Hera comes from a European heritage in innovative lighting design and technology and as manufacturers develop our own unique lighting systems.

Hera's expertise in bringing new trends and technology to the market has been evident throughout the decades. As a driving force in lighting technology, Hera's main focus for more than a decade has been LED technology -- bringing energy-efficient and maintenance free LEDs to market.

All Hera lighting products are unique, stylishly designed and on the leading edge of today's lighting technology, with lighting systems that exemplify beauty as well as form and function.



HERA LIGHTING



# STICK 2 LED

## MINI LINEAR LED WITH INTEGRATED CONNECTING SYSTEM

- Aluminum and plexiglass housing
- Recess or surface mount
- 50,000 hr. life
- Dimmable with optional accessories (consult factory)
- Uses: furniture, cabinets, displays, closets, food cases

3000K	Watt	Lumens	L	W	D
STICK2/8/WW	1.6	80	8"	7/16"	3/8"
STICK2/12/WW	2.4	109	12"	7/16"	3/8"
STICK2/34/WW	7.2	341	34"	7/16"	3/8"
STICK2/46/WW	9.7	461	46"	7/16"	3/8"

4100K	Watt	Lumens	L	W	D
STICK2/8/CW	1.6	70	8"	7/16"	3/8"
STICK2/12/CW	2.4	107	12"	7/16"	3/8"
STICK2/34/CW	7.2	304	34"	7/16"	3/8"
STICK2/46/CW	9.7	411	46"	7/16"	3/8"

Accessories	
STICK2/PC	Power cord 98"
STICK2/CC1	1" connecting cable
STICK2/CC12	12" connecting cable
STICK2/CC39	39" connecting cable
STICK/TB	Terminal block
KBI2LEDCC39	39" power cable
KBI2LEDCC98	98" power cable

Drivers	
STICKPS24/6WATT	6 watt
STICKPS24/30HE	30 watt
STICKPS24/75	75 watt
STICKPS24/96/DIM	96 watt



# STICK 3 LED

## MINI LINEAR LED WITH INTEGRATED CONNECTING SYSTEM

- Aluminum housing
- Frosted light lens
- Recess or surface mount
- 50,000 hr. life
- Dimmable with optional accessories (consult factory)
- Uses: furniture, cabinets, displays, show cases

3000K	Watt	Lumens	L	W	D
STICK3/8/WW	2.5	260	7-7/8"	1/2"	1/2"
STICK3/12/WW	4	420	11-13/16"	1/2"	1/2"
STICK3/24/WW	7.5	840	22-7/16"	1/2"	1/2"
STICK3/34/WW	11.5	1260	34-1/4"	1/2"	1/2"
STICK3/46/WW	15	1680	44-7/8"	1/2"	1/2"

4100K	Watt	Lumens	L	W	D
STICK3/8/CW	2.5	260	7-7/8"	1/2"	1/2"
STICK3/12/CW	4	420	11-13/16"	1/2"	1/2"
STICK3/24/CW	7.5	840	22-7/16"	1/2"	1/2"
STICK3/34/CW	11.5	1260	34-1/4"	1/2"	1/2"
STICK3/46/CW	15	1680	44-7/8"	1/2"	1/2"

Accessories	
STICK3/PC	Power cord 59"
STICK3/CC2	2" connecting cable
STICK3/CC12	12" connecting cable
STICK3/CC39	39" connecting cable
STICK/TB	Terminal block
KBI2LEDCC39	39" power cable
KBI2LEDCC98	98" power cable

Drivers	
STICKPS24/6WATT	6 watt
STICKPS24/30HE	30 watt
STICKPS24/75	75 watt
STICKPS24/96/DIM	96 watt





## ELITE LED

### LINEAR LED WITH DIRECT CONNECT SYSTEM

- Aluminum housing with frosted lens
- Recess or surface mount
- 50,000 hr. life
- Uses: furniture, cabinets, displays

3000K	Watt	Lumens	L	W	D
EL/LED/12/WW	5	320	11"	1"	1-3/8"
EL/LED/22/WW	9	700	21-3/16"	1"	1-3/8"
EL/LED/34/WW	12	950	33"	1"	1-3/8"
EL/LED/46/WW	15	1200	44-13/16"	1"	1-3/8"
EL/LED/59/WW	18	1550	56-5/8"	1"	1-3/8"

#### Accessories

Connecting cables from 6" to 144"  
Straight or 90°

#### Power Cords

With plug from 36" to 144"

4100K	Watt	Lumens	L	W	D
EL/LED/12/CW	5	320	11"	1"	1-3/8"
EL/LED/22/CW	9	700	21-3/16"	1"	1-3/8"
EL/LED/34/CW	12	950	33"	1"	1-3/8"
EL/LED/46/CW	15	1200	44-13/16"	1"	1-3/8"
EL/LED/59/CW	18	1550	56-5/8"	1"	1-3/8"

Consult factory



## SLIMLITE XL T5

### LINEAR FLUORESCENT WITH DIRECT CONNECT SYSTEM

- Steel housing and aluminum with optional lens (order separately)
- Surface mount
- Energy efficient T5 lamps (order separately)
- Electronic ballast
- Uses: shelves, cabinets, displays, food applications

White	Lamp	Lumens	L	W	H
ES12/R	F8WT5	400	12-7/8"	7/8"	1-5/16"
ES22/R	F14WT5	1350	23-1/8"	7/8"	1-5/16"
ES34/R	F21T5	2100	34-7/8"	7/8"	1-5/16"
ES46/R	F28T5	2900	46-3/4"	7/8"	1-5/16"
ES59/R	F35T5	3650	58-7/16"	7/8"	1-5/16"

#### Accessories

SCC6/XL/R 6" connecting cable  
 SCC12/XL/R 12" connecting cable  
 SCC24/XL/R 24" connecting cable  
 SCC48/XL/R 48" connecting cable  
 SCC72/XL/R 72" connecting cable  
 SCC120/XL/R 120" connecting cable  
 SDC/XL/R Direct connect

#### Power Cords

SPC/XL/R 72"  
 SPC/S/XL/R 72" with roller switch  
 SPC72/STC 72" with straight connector





# R55

## LED SPOTLIGHT

- Aluminum housing
- Recess or surface mount
- 50,000 hr. life
- Dimmable with optional accessories (consult factory)
- Uses: furniture, cabinets, displays

3000K	Color	Watt	Lumens	Dia	D
R55-LED/SS/WW	Stainless Steel	3	165	2-11/16"	7/16"
R55-LED/CH/WW	Matte Chrome	3	165	2-11/16"	7/16"
R55-LED/BL/WW	Black	3	165	2-11/16"	7/16"
R55-LED/WH/WW	White	3	165	2-11/16"	7/16"

4100K	Color	Watt	Lumens	Dia	D
R55-LED/SS/CW	Stainless Steel	3	165	2-11/16"	7/16"
R55-LED/CH/CW	Matte Chrome	3	165	2-11/16"	7/16"
R55-LED/BL/CW	Black	3	165	2-11/16"	7/16"
R55-LED/WH/CW	White	3	165	2-11/16"	7/16"

Accessories	
STICK/TB	Terminal block
KB12LEDCC39	39" power cable
KB12LEDCC98	98" power cable

Drivers	
STICKPS24/6WATT	6 watt
STICKPS24/30HE	30 watt
STICKPS24/75	75 watt
STICKPS24/96/DIM	96 watt



# FR68

## LED SPOTLIGHT

- Aluminum housing with frosted lens
- Recess or surface mount
- 50,000 hr. life
- Dimmable with optional accessories (consult factory)
- Uses: furniture, cabinets, displays

3000K	Color	Watt	Lumens	Dia	D
FR68/SS/3000	Stainless Steel	4	230	2-15/16"	9/16"
FR68/MC/3000	Matte Chrome	4	230	2-15/16"	9/16"

4000K	Color	Watt	Lumens	Dia	D
FR68/SS/4000	Stainless Steel	4	230	2-15/16"	9/16"
FR68/MC/4000	Matte Chrome	4	230	2-15/16"	9/16"

Accessories	
STICK/TB	Terminal block
KB12LEDCC39	39" power cable
KB12LEDCC98	98" power cable


Drivers	
STICKPS24/6WATT	6 watt
STICKPS24/30HE	30 watt
STICKPS24/75	75 watt
STICKPS24/96/DIM	96 watt





## EYE-LED LED MINI SPOTLIGHT

- Aluminum housing
- Recess mount
- 50,000 hr. life
- Dimmable with optional accessories (consult factory)
- Uses: furniture, cabinets, displays, closets



3000K		Color	Watt	Lumens	Dia	D	Accessories	
EYELEDSS/WW	Stainless Steel	1	60	1-1/8"	1/2"	LEDCC36	36" connecting cable	
EYELEDA/WW	Aluminum	1	60	1-1/8"	1/2"	LEDCC72	72" connecting cable	
						TBLED/B	Terminal block	
4000K		Color	Watt	Lumens	Dia	D	Drivers	
EYELEDSS/CW	Stainless Steel	1	80	1-1/8"	1/2"	PSLED10	10 watt	
EYELEDA/CW	Aluminum	1	80	1-1/8"	1/2"	PSLED/DIM/S	18 watt dimmable	
						DIMCONTROL	LED dimmer control	

# SR68

## LED SWIVEL SPOTLIGHT

- Aluminum housing with frosted lens
- Recess mount with 20° swivel and tilt
- 50,000 hr. life
- Dimmable with optional accessories (consult factory)
- Uses: furniture, cabinets, displays, closets

3000K	Color	Watt	Lumens	Dia	D
SR68/WW	Brushed Aluminum	4.8	283	3-3/16"	1-9/16"

4000K	Color	Watt	Lumens	Dia	D
SR68/CW	Brushed Aluminum	4.8	283	3-3/16"	1-9/16"

Accessories	
LEDCC36	36" connecting cable
LEDCC72	72" connecting cable

Drivers	
PSLED/10	10 watt
PSLED/DIM/S	18 watt dimmable
DIMCONTROL	LED dimmer control



# SR45

## LED SWIVEL SPOTLIGHT

- Aluminum housing
- Recess mount with 20° swivel and tilt
- 50,000 hr. life
- Dimmable with optional accessories (consult factory)
- Uses: furniture, cabinets, displays, closets

3000K	Color	Watt	Lumens	Dia	D
SR45/SS/3000	Stainless Steel	5.3	422	2"	1-1/4"
SR45/WH/3000	White	5.3	422	2"	1-1/4"

4000K	Color	Watt	Lumens	Dia	D
SR45/SS/4000	Stainless Steel	5.3	422	2"	1-1/4"
SR45/WH/4000	White	5.3	422	2"	1-1/4"

Accessories	
LEDCC36	36" connecting cable
LEDCC72	72" connecting cable

Drivers	
PSLED/10	10 watt
PSLED/DIM/S	18 watt dimmable
DIMCONTROL	LED dimmer control






# [✓] MP LIGHTING®

AFX Partner

As AFX's strategic partner, MP Lighting® furthers our continued commitment to bring design, technology and ever-increasing value to our lighting partners.

MP's focus is innovative design technologies that keeps their products at the forefront of technology in the Commercial/Consumer lighting industry, specializing in manufacturing specification-grade architectural LED fixtures, as well as Low Voltage, Line Voltage, and Multi-Circuit Track Systems.

Established in 1994, MP Lighting is a Canadian owned and operated company with headquarters in Vancouver, BC. Products are suited for commercial, institutional, industrial, hospitality, and residential applications.





## L01 IN-GRADE ACCENT LIGHT

- Exterior/Interior Grade
- IP68 Wet location listed
- Tempered clear glass lens, 30° beam spread
- Splice box, aluminum flange and level gauge (included)
- Dimmable with 12V AC power supply\* (not included)
- Uses: stairs, ramps, aisle installation

Stainless	Watt	Lumens	CCT	Dia	D
L01-1W27SNCOAS0-S6	1	58	2700K	2-1/4"	1-3/4"
L01-2W27SNCOAS0-S6	2.5	78	2700K	2-1/4"	1-3/4"
<b>Matte Clear Anodized</b>					
L01-1W27SNCOAS0-MA	1	58	2700K	2-1/4"	1-3/4"
L01-2W27SNCOAS0-MA	2.5	78	2700K	2-1/4"	1-3/4"
<b>Bronze</b>					
L01-1W27SNCOAS0-BZ	1	58	2700K	2-1/4"	1-3/4"
L01-2W27SNCOAS0-BZ	2.5	78	2700K	2-1/4"	1-3/4"

\*TLW120MT050-01 — recommended Dimmable Power Supply (order separately)



## L02 IN-GRADE ACCENT LIGHT

- Interior Grade
- IP53 Dry location listed
- Tempered clear glass lens, 30° beam spread
- Steel flange (included)
- Dimmable with 12V AC power supply\* (not included)
- Uses: stairs, ramps, aisle installation

Stainless	Watt	Lumens	CCT	Dia	D
L02-1W27SNCOA-S6	1	58	2700K	2-1/4"	1-3/4"
L02-2W27SNCOA-S6	2.5	78	2700K	2-1/4"	1-3/4"
<b>Matte Clear Anodized</b>					
L02-1W27SNCOA-MA	1	58	2700K	2-1/4"	1-3/4"
L02-2W27SNCOA-MA	2.5	78	2700K	2-1/4"	1-3/4"
<b>Bronze</b>					
L02-1W27SNCOA-BZ	1	58	2700K	2-1/4"	1-3/4"
L02-2W27SNCOA-BZ	2.5	78	2700K	2-1/4"	1-3/4"

\*TLW120MT050-01 — recommended Dimmable Power Supply (order separately)



## L06 IN-GRADE ACCENT LIGHT

- Exterior/Interior Grade
- IP68 Wet location listed
- Tempered frosted glass lens
- Can be ordered with mounting box (B) or without (N)
- Uses: driveways, sidewalks

Stainless	Watt	Lumens	CCT	Dia	D
L06-WWHSFB2-S6	0.2	2.1	2700K	4-7/8"	2-1/2"
L06-WWHSFB4-S6	0.2	2.1	2700K	4-7/8"	4"
L06-WWHSFB8-S6	0.2	2.1	2700K	4-7/8"	8"
L06-WWHSFN2-S6	0.2	2.1	2700K	4-7/8"	2-1/2"
L06-WWHSFN4-S6	0.2	2.1	2700K	4-7/8"	4"
L06-WWHSFN8-S6	0.2	2.1	2700K	4-7/8"	8"

\*TLDDL10W12V1 — recommended NON-Dimmable Power Supply (order separately)





## L07 IN-GRADE ACCENT LIGHT

- Exterior/Interior Grade
- IP67 Wet location listed
- Tempered clear (C) or frosted (F) glass lens
- Uses: deck flooring

Stainless	Watt	Lumens	CCT	Dia	D
L07-WWHC-S6	0.2	2.1	2700K	3/4"	1-1/2"
L07-WWHF-S6	0.2	2.1	2700K	3/4"	1-1/2"

\*TLDDL10W12V1 – recommended NON-Dimmable Power Supply (order separately)

## L08 IN-GRADE ACCENT LIGHT

- Exterior/Interior Grade
- IP68 Wet location listed
- Tempered clear glass lens, single or double aperture
- Back box, aluminum flange and level gauge (included)
- Dimmable with 12V AC power supply\* (not included)
- Uses: uplight walls, columns, architectural features



Stainless	Apertures	Watt	Lumens	CCT	Dia	D
L08-1W27SSASO-S6	Single	1	0.5	2700K	2-7/16"	2"
L08-1W27SDASO-S6	Double	1	1	2700K	2-7/16"	2"
L08-2W27SSASO-S6	Single	2.5	0.8	2700K	2-7/16"	2"
L08-2W27SDASO-S6	Double	2.5	1.5	2700K	2-7/16"	2"
<b>Matte Clear Anodized</b>						
L08-1W27SSASO-MA	Single	1	0.5	2700K	2-7/16"	2"
L08-1W27SDASO-MA	Double	1	1	2700K	2-7/16"	2"
L08-2W27SSASO-MA	Single	2.5	0.8	2700K	2-7/16"	2"
L08-2W27SDASO-MA	Double	2.5	1.5	2700K	2-7/16"	2"
<b>Bronze</b>						
L08-1W27SSASO-BZ	Single	1	0.5	2700K	2-7/16"	2"
L08-1W27SDASO-BZ	Double	1	1	2700K	2-7/16"	2"
L08-2W27SSASO-BZ	Single	2.5	0.8	2700K	2-7/16"	2"
L08-2W27SDASO-BZ	Double	2.5	1.5	2700K	2-7/16"	2"

\*TLW120MT050-01 – recommended Dimmable Power Supply (order separately)

## L09 IN-GRADE ACCENT LIGHT

- Interior Grade
- IP53 Dry location listed
- Tempered clear glass lens, single or double aperture
- Back box, aluminum flange and level gauge (included)
- Dimmable with 12V AC power supply\* (not included)
- Uses: uplight walls, columns, architectural features



Stainless	Apertures	Watt	Lumens	CCT	Dia	D
L09-1W27SSA-S6	Single	1	0.5	2700K	2-3/8"	2"
L09-1W27SDA-S6	Double	1	1	2700K	2-3/8"	2"
L09-2W27SSA-S6	Single	2.5	0.8	2700K	2-3/8"	2"
L09-2W27SDA-S6	Double	2.5	1.5	2700K	2-3/8"	2"
<b>Matte Clear Anodized</b>						
L09-1W27SSA-MA	Single	1	0.5	2700K	2-3/8"	2"
L09-1W27SDA-MA	Double	1	1	2700K	2-3/8"	2"
L09-2W27SSA-MA	Single	2.5	0.8	2700K	2-3/8"	2"
L09-2W27SDA-MA	Double	2.5	1.5	2700K	2-3/8"	2"
<b>Bronze</b>						
L09-1W27SSA-BZ	Single	1	0.5	2700K	2-3/8"	2"
L09-1W27SDA-BZ	Double	1	1	2700K	2-3/8"	2"
L09-2W27SSA-BZ	Single	2.5	0.8	2700K	2-3/8"	2"
L09-2W27SDA-BZ	Double	2.5	1.5	2700K	2-3/8"	2"

\*TLW120MT050-01 – recommended Dimmable Power Supply (order separately)



## L300 IN-GRADE ACCENT LIGHT

- Exterior/Interior Grade
- IP66 Wet location listed
- Tempered clear glass lens, 30° beam spread
- Splice box, aluminum flange and level gauge (included)
- Dimmable with 12V AC power supply\* (not included)
- Uses: stairs, ramps, aisle installation

Stainless	Watt	Lumens	CCT	Dia	D
L300-1W27SNCOASO-S6	1	31	2700K	2-1/2"	2"
L300-2W27SNCOASO-S6	2.5	50	2700K	2-1/2"	2"
<b>Matte Clear Anodized</b>					
L300-1W27SNCOASO-MA	1	31	2700K	2-1/2"	2"
L300-2W27SNCOASO-MA	2.5	50	2700K	2-1/2"	2"
<b>Bronze</b>					
L300-1W27SNCOASO-BZ	1	31	2700K	2-1/2"	2"
L300-2W27SNCOASO-BZ	2.5	50	2700K	2-1/2"	2"

\*TLW120MT050-01 — recommended Dimmable Power Supply (order separately)



## L304 IN-GRADE ACCENT LIGHT

- Square Exterior/Interior Grade
- IP66 Wet location listed
- Tempered clear glass lens, 30° beam spread
- Splice box, aluminum flange and level gauge (included)
- Dimmable with 12V AC power supply\* (not included)
- Uses: upright walls, columns, architectural features

Stainless	Watt	Lumens	CCT	L	W	D
L304-1W27SNCOAS-S6	1	31	2700K	2-1/4"	2-1/4"	1-7/16"
L304-2W27SNCOAS-S6	2.5	50	2700K	2-1/4"	2-1/4"	1-7/16"
<b>Matte Clear Anodized</b>						
L304-1W27SNCOAS-MA	1	31	2700K	2-1/4"	2-1/4"	1-7/16"
L304-2W27SNCOAS-MA	2.5	50	2700K	2-1/4"	2-1/4"	1-7/16"
<b>Bronze</b>						
L304-1W27SNCOAS-BZ	1	31	2700K	2-1/4"	2-1/4"	1-7/16"
L304-2W27SNCOAS-BZ	2.5	50	2700K	2-1/4"	2-1/4"	1-7/16"

\*TLW120MT050-01 — recommended Dimmable Power Supply (order separately)



## L337 IN-GRADE ACCENT LIGHT

- Exterior/Interior Grade
- IP67 Wet location listed
- Tempered clear (C) or frosted (F) glass lens
- Uses: ceiling mount light

Stainless	Watt	Lumens	CCT	Dia	D
L337-WWHSC-S6	0.2	2.1	2700K	7/8"	1-3/8"
L337-WWHSF-S6	0.2	2.1	2700K	7/8"	1-3/8"

\*TLDDL10W12V1 — recommended NON-Dimmable Power Supply (order separately)





## L302

### IN-GRADE ACCENT LIGHT

- Trimless Exterior/Interior Grade
- IP66 Wet location listed
- Tempered clear glass lens, 30° beam spread
- Splice box, aluminum flange and level gauge (included)
- Dimmable with 12V AC power supply\* (not included)
- Uses: uplight walls, columns, architectural features

Stainless	Watt	Lumens	CCT	Dia	D
L302-1W27SNA0S-S6	1	58	2700K	1-3/4"	1-7/16"
L302-2W27SNA0S-S6	2.5	78	2700K	1-3/4"	1-7/16"
Matte Clear Anodized					
L302-1W27SNA0S-MA	1	58	2700K	1-3/4"	1-7/16"
L302-2W27SNA0S-MA	2.5	78	2700K	1-3/4"	1-7/16"
Bronze					
L302-1W27SNA0S-BZ	1	58	2700K	1-3/4"	1-7/16"
L302-2W27SNA0S-BZ	2.5	78	2700K	1-3/4"	1-7/16"



\*TLW120MT050-01 — recommended Dimmable Power Supply (order separately)

# L46

## WALL MOUNT



- Exterior/Interior Grade
- IP66 Wet location listed
- Polycarbonate lens
- Non-dimmable with 12V DC power supply (included)
- Uses: stairs, ramps, aisle, walkway installation

	Watt	Lumens	CCT	H	W	D
<b>Stainless</b>						
L46-3W30SD-S6	3	28	3000K	3-3/8"	5"	3/8"
L46-6W30SD-S6	6	50	3000K	3-3/8"	5"	3/8"
<b>Matte Clear Anodized</b>						
L46-3W30SD-MA	3	28	3000K	3-3/8"	5"	3/8"
L46-6W30SD-MA	6	50	3000K	3-3/8"	5"	3/8"
<b>Bronze</b>						
L46-3W30SD-BZ	3	28	3000K	3-3/8"	5"	3/8"
L46-6W30SD-BZ	6	50	3000K	3-3/8"	5"	3/8"

# L47

## WALL MOUNT



- Exterior/Interior Grade
- IP66 Wet location listed
- Polycarbonate lens
- Non-dimmable with 12V DC power supply (included)
- Uses: stairs, ramps, aisle, walkway installation

	Watt	Lumens	CCT	H	W	D
<b>Stainless</b>						
L47-3W30SD-S6	3	28	3000K	5"	3-3/8"	3/8"
L47-6W30SD-S6	6	50	3000K	5"	3-3/8"	3/8"
<b>Matte Clear Anodized</b>						
L47-3W30SD-MA	3	28	3000K	5"	3-3/8"	3/8"
L47-6W30SD-MA	6	50	3000K	5"	3-3/8"	3/8"
<b>Bronze</b>						
L47-3W30SD-BZ	3	28	3000K	5"	3-3/8"	3/8"
L47-6W30SD-BZ	6	50	3000K	5"	3-3/8"	3/8"

# L49

## WALL MOUNT



- Exterior/Interior Grade
- IP66 Wet location listed
- Polycarbonate lens
- Adjustable 30° tilt light, 60° beam spread
- Dimmable with 19.2V DC power supply (included)
- Uses: stairs, ramps, aisle, walkway installation

	Watt	Lumens	CCT	H	W	D
<b>Stainless</b>						
L49-6W27S0A-S6	6	112	2700K	4-7/8"	9-3/4"	1/2"
<b>Matte Clear Anodized</b>						
L49-6W27S0A-MA	6	112	2700K	4-7/8"	9-3/4"	1/2"
<b>Bronze</b>						
L49-6W27S0A-BZ	6	112	2700K	4-7/8"	9-3/4"	1/2"



MP LIGHTING





# L13

## WALL MOUNT

- Interior Grade
- IP50 Dry location listed
- Tempered clear glass lens, 30° beam spread
- Non-dimmable with 3.2V DC power supply (included)
- Uses: stairs, ramps, aisle, walkway installation

Matte Chrome	Mounting	Watt	Lumens	CCT	H	W	D
L13-1W27HNVA-MC	Vertical	1	43	2700K	4-3/4"	3-1/8"	1-1/4"
L13-2W27HNVA-MC	Vertical	2.5	88	2700K	4-3/4"	3-1/8"	1-1/4"
L13-1W27HNHA-MC	Horizontal	1	43	2700K	4-3/4"	3-1/8"	1-1/4"
L13-2W27HNHA-MC	Horizontal	2.5	88	2700K	4-3/4"	3-1/8"	1-1/4"
<b>Black</b>							
L13-1W27HNVA-BK	Vertical	1	43	2700K	4-3/4"	3-1/8"	1-1/4"
L13-2W27HNVA-BK	Vertical	2.5	88	2700K	4-3/4"	3-1/8"	1-1/4"
L13-1W27HNHA-BK	Horizontal	1	43	2700K	4-3/4"	3-1/8"	1-1/4"
L13-2W27HNHA-BK	Horizontal	2.5	88	2700K	4-3/4"	3-1/8"	1-1/4"
<b>Brushed Nickel</b>							
L13-1W27HNVA-BN	Vertical	1	43	2700K	4-3/4"	3-1/8"	1-1/4"
L13-2W27HNVA-BN	Vertical	2.5	88	2700K	4-3/4"	3-1/8"	1-1/4"
L13-1W27HNHA-BN	Horizontal	1	43	2700K	4-3/4"	3-1/8"	1-1/4"
L13-2W27HNHA-BN	Horizontal	2.5	88	2700K	4-3/4"	3-1/8"	1-1/4"
<b>White</b>							
L13-1W27HNVA-WH	Vertical	1	43	2700K	4-3/4"	3-1/8"	1-1/4"
L13-2W27HNVA-WH	Vertical	2.5	88	2700K	4-3/4"	3-1/8"	1-1/4"
L13-1W27HNHA-WH	Horizontal	1	43	2700K	4-3/4"	3-1/8"	1-1/4"
L13-2W27HNHA-WH	Horizontal	2.5	88	2700K	4-3/4"	3-1/8"	1-1/4"



# L16

## WALL MOUNT

- Exterior/Interior Grade
- IP66 Wet location listed
- Tempered clear glass lens, 30° beam spread
- Non-dimmable with 3.2V DC power supply (included)
- Uses: stairs, ramps, aisle, walkway installation

Stainless	Watt	Lumens	CCT	H	W	D
L16-1W27SNVD-S6	1	43	2700K	5"	3-3/8"	2-5/8"
L16-2W27SNVD-S6	2.5	97	2700K	5"	3-3/8"	2-5/8"



# L17

## WALL MOUNT

- Exterior/Interior Grade
- IP66 Wet location listed
- Tempered clear glass lens, 30° beam spread
- Non-dimmable with 6.4V DC power supply (included)
- Uses: stairs, ramps, aisle, walkway installation

Stainless	Watt	Lumens	CCT	H	W	D
L17-1W27SNVD-S6	1	109	2700K	5"	3-3/8"	2-5/8"
L17-2W27SNVD-S6	2.5	175	2700K	5"	3-3/8"	2-5/8"

# L22

## WALL MOUNT

- Exterior/Interior Grade
- IP66 Wet location listed
- Polycarbonate lens
- Non-dimmable with 3.2V DC power supply (included)
- Uses: stairs, ramps, aisle, walkway installation

Stainless	Watt	Lumens	CCT	H	D
L22-1W27SFD-S3	1	14	2700K	4-5/8"	3/4"
L22-2W27SNVD-S3	2.5	28	2700K	4-5/8"	3/4"



# L720

## WALL MOUNT

- Exterior/Interior Grade
- IP66 Wet location listed
- Tempered clear glass lens, 30° beam spread
- Non-dimmable with 12V DC power supply (included)
- Uses: stairs, ramps, aisle, walkway installation

Matte Clear Anodized	Watt	Lumens	CCT	H	Dia
L720-16W27SNC-MA	16	614	2700K	8-1/2"	4"



# L721

## WALL MOUNT

- Exterior/Interior Grade
- IP66 Wet location listed
- Tempered clear glass lens, 30° beam spread
- Non-dimmable with 12V DC power supply (included)
- Uses: stairs, ramps, aisle, walkway installation

Matte Clear Anodized	Watt	Lumens	CCT	H	Dia
L721-8W27SNC-MA	8	307	2700K	4-7/8"	4"





## L500 CABINET LIGHT

- Interior Grade
- IP20 Dry location listed
- Friction fit spring clips
- Tempered clear glass lens, 30° beam spread
- Powered by remote dimmable DC power supply\* (not included)
- Uses: showcases, cabinets, millwork

Stainless	Watt	Lumens	CCT	L	W	D
L500-2W27SSND-MA	2.5	106	2700K	2-1/4"	2-1/4"	1-1/2"

\*Recommended driver LED18W700iB for 2 to 6 fixtures in series



## L501 CABINET LIGHT

- Interior Grade
- IP20 Dry location listed
- Friction fit spring clips
- Tempered clear glass lens, 30° beam spread
- Powered by remote dimmable DC power supply\* (not included)
- Uses: showcases, cabinets, millwork

Matte Clear Anodized	Watt	Lumens	CCT	Dia	D
L501-2W27SSND-MA	2.5	108	2700K	2-1/2"	1-1/2"

\*Recommended driver LED18W700iB for 2 to 6 fixtures in series

# L182

## WINE RACK

- Interior Grade - black anodized
- IP40 Dry location listed
- Wall mount, non-UV
- 30° beam spread
- Dimmable with 12V AC power supply\* (not included) / 1 fixture in series, 1-25 legs in parallel
- Dimmable with DC driver\* (not included) / 2-12 fixtures connected in a series
- Uses: restaurants, bars, wine cellars


### Rack Arms

Black Anodized	Arm	Accessories	CrossBar	Watt	Lumens	CCT	L	W	D
L182T-W27HNHSA-BA	Top	Half Shroud	NA	1	64	2700K	NA	8"	8-1/4"
L182M-W27HNHSA1A-BA	Middle	Half Shroud	Single Neck View	1	64	2700K	NA	3-1/2"	8-1/4"
L182M-W27HNHSA2A-BA	Middle	Half Shroud	Double Neck View	1	64	2700K	NA	5-7/8"	8-1/4"
L182M-W27HNHSA1B-BA	Middle	Half Shroud	Single Front View	1	64	2700K	NA	8"	8-1/4"
L182M-W27HNHSA2B-BA	Middle	Half Shroud	Double Front View	1	64	2700K	NA	8"	8-1/4"
L182B-1A-BA	Bottom	NA	Single Neck View	NA	NA	NA	NA	3-1/2"	8-1/4"
L182B-2A-BA	Bottom	NA	Double Neck View	NA	NA	NA	NA	5-7/8"	8-1/4"
L182B-1B-BA	Bottom	NA	Single Front View	NA	NA	NA	NA	8"	8-1/4"
L182B-2B-BA	Bottom	NA	Double Front View	NA	NA	NA	NA	8"	8-1/4"

### Rack Rail

Black Anodized	L	W	D
RAL182-2-WR-MB-BA	24"	1-1/4"	1"
RAL182-3-WR-MB-BA	36"	1-1/4"	1"
RAL182-4-WR-MB-BA	48"	1-1/4"	1"
RAL182-5-WR-MB-BA	60"	1-1/4"	1"
RAL182-6-WR-MB-BA	72"	1-1/4"	1"
RAL182-7-WR-MB-BA	84"	1-1/4"	1"
RAL182-8-WR-MB-BA	96"	1-1/4"	1"

Recommended\*  
 TLW120MT050-01 (AC) Dimmable Power Supply  
 LED18W350i (DC) Dimmable Power Supply  
 (Order separately)



MP LIGHTING





# Custom Capabilities

Making your vision a reality.

---

At AFX, we appreciate that every space and application is unique to each designer's vision. To accommodate flexibility and creativity, AFX product lines are engineered with the idea that they can be customized to satisfy each client's project requirements.

If you don't see the exact solution from among our standard product offerings, AFX gives you the freedom to create your own lighting solution. From stock to modifications to full custom, we offer numerous options to meet your specific needs. To support projects requiring quick turnaround, we also maintain sufficient inventory levels on many items to meet job quantity requirements.


The **Standard Product Modification Program** is designed to offer modification flexibility on selected standard products to meet a specific need.

Customizable options include finish, shade, glass, color, ballast type and lamping. Typical lead time from receipt of order is 4 - 8 weeks.

The **Custom Program** takes collaboration to a higher level. We work more closely with "you" the interior designer, architect, lighting designer, and specifier to develop custom lighting solutions specific to your needs. A drawing, photo or description of the fixture concept is all we need to get started. From there, our team will work with you and your customer to create a one-of-a-kind lighting solution. Typical lead time is 12 weeks from order receipt and drawing approval.



**Lumafuse™ Fabrics**



Black (BK)




Linen White (LW)




Jute (JT)

**Wood Finishes**




Espresso (ES)



Weathered Grey (WG)

**Veneer Finishes**




Chocolate Oak (CV)



Grey (GV)

**Painted Colors**



Black (BK)




White (WH)




Silver (SL)


**Metal Finishes**



Oakley Bronze (KB)



Satin Nickel (SN)




Oil-Rubbed Bronze (RB)



Chrome (PC)

**Expanded Painted Colors** (minimum quantities/set-up fees apply)



Purple (PU)



Green (GN)



Blue (BU)



Bronze (BZ)



Copper (CU)



Gold (GD)



Red (RD)















































Orange (OG)

*Custom fabric and finishes available, consult factory.*

# Lamp Equivalency

The chart below gives the general comparison of fluorescent lamps to the incandescent lamps listed on the left.

## Incandescent to Fluorescent Lamp Equivalency

INCANDESCENT:	SINGLE CFL	SINGLE GU24	MULTIPLE CFL	MULTIPLE GU24	T9 CIRCLINE	T5 CIRCLINE	LINEAR FLUORESCENT
<b>4,000-5,000 lumens</b>  3 x 100 watt 5,070 lumens					 32W & 40W Circline 15,000 hrs & 18,000 hrs <b>4,750 lumens</b>	 22W & 40W Circline 12,000 hrs <b>5,000 lumens</b>	 2 x 32W T8 Straight Tube (48") 20,000 hrs. <b>5,600 lumens</b>
<b>3,500 lumens</b>  2 x 100 watt 3,380 lumens			 2 x 26W Quad CFL <b>3,420 lumens</b>	 2 x 26W GU24 <b>3,600 lumens</b>	 22W & 32W Circline 12,000 hrs & 15,000 hrs <b>3,000 lumens</b>	 70W 2C Circline 10,000 hrs <b>4,600 lumens</b>	
<b>3,000 lumens</b>  150W A19 750 hrs 2,850 lumens	 24W PL-L CFL Electronic 4-pin 15,000 hrs <b>1,800 lumens</b>	 26W GU24 10,000 hrs <b>1,800 lumens</b>	 2 x 18W Quad CFL <b>2,300 lumens</b>	 2 x 18W GU24 <b>2,700 lumens</b>	 40W Circline 18,000 <b>2,800 lumens</b>	 55W Circline 12,000 hrs <b>4,000 lumens</b>	 28W T5 Straight Tube (46") 25,000 hrs <b>2,900 lumens</b>
<b>2,500 lumens</b>  2 x 60 watt 1,700 lumens	 26W Quad CFL Electronic 4-pin 12,000 hrs <b>1,710 lumens</b>		 2 x 13W Quad CFL <b>2,800 lumens</b>	 2 x 13W GU24 <b>1,900 lumens</b>	 32W Circline 15,000 hrs <b>1,950 lumens</b>	 55W 2C Circline 10,000 hrs <b>3,900 lumens</b>	 32W T8 Straight Tube (48") 20,000 hrs <b>2,800 lumens</b>
<b>2,000 lumens</b>  2 x 60 watt 1,700 lumens		 25W GU24 Dim 8,000 hrs <b>1,600 lumens</b>					 21W T5 Straight Tube (34") 25,000 hrs <b>2,100 lumens</b>
<b>2,000 lumens</b>  100W A19 750 hrs 1,690 lumens		 18W GU24 10,000 hrs <b>1,350 lumens</b>					 25W T8 Straight Tube (36") 20,000 hrs <b>2,050 lumens</b>
<b>1,500 lumens</b>  75W A19 750 hrs 1,170 lumens	 18W Quad CFL Electronic 4-pin 12,000 hrs <b>1,150 lumens</b>						 14W T5 Straight Tube (22") 25,000 hrs <b>1,350 lumens</b>
<b>1,000 lumens</b>  60W A19 1000 hrs 850 lumens	 13W Quad CFL Electronic 4-pin 12,000 hrs <b>900 lumens</b>	 13W GU24 10,000 hrs <b>950 lumens</b>			 22W Circline 12,000 hrs <b>1,050 lumens</b>		 17W T8 Straight Tube (24") 20,000 hrs <b>1,325 lumens</b>
<b>500 lumens</b>  40W A19 1500 hrs 495 lumens	 13W Twin Tube CFL 10,000 hrs <b>800 lumens</b>						 15W T8 Straight Tube (18") 20,000 hrs <b>870 lumens</b>
<b>400 lumens</b>  25W A19 1000 hrs 320 lumens							 8W T5 Straight Tube (12") 7,500 hrs <b>450 lumens</b>
							 6W T5 Straight Tube (9") 7,500 hrs <b>325 lumens</b>

\*This chart is for general comparison only. Light output shown is initial lumens as published by Osram Sylvania and MaxLite. Ballast factors are not considered.



## LED Evolution

LED's (light-emitting diodes) bring several advantages to the lighting industry, including high efficacy and durability. With superior life over other lamp sources (50,000 hours+), the required maintenance for LED products is greatly reduced. This translates into energy savings and environmental sustainability. LEDs create greater optical control (more controllable source), dimming, instant on/off, and reduced rate of lumen depreciation (potential for long application life).

The use of LED luminaires in commercial and residential applications is viable today both economically and from an illumination performance standpoint. The advances in LED technology allow AFX to bring these products to the marketplace via retrofitting, hybrid or new designs to meet a variety of lighting applications.

**If the fixture you are seeking does not currently offer an LED option, consult the factory for availability.**

### LED Features and Benefits

**Long-lasting**—LEDs last up to 5 times longer than compact fluorescents, and far longer than typical incandescent lamps. Average LED lamp life: 50,000 hrs.

**Cold weather**—Excellent for use in cold climates.

**Durable**—Since LEDs do not have filament, they are not damaged under circumstances when regular incandescent bulb would be broken.

**Instant-On**—LED fixtures turn on instantly in all weather conditions.

**Cool**—LEDs produce 3.4 btu's/hour, compared to 85 btu's for incandescent bulbs.

**Mercury-free**—No mercury is used in the manufacturing of LEDs.

**More efficient**—LEDs use only 2-10 watts of electricity (1/3rd to 1/30th of incandescent or CFL).

**Cost effective**—Although LEDs are more expensive than CFL or incandescent, the cost is recouped over time in energy savings, maintenance reduction and little to no replacement costs.



### LED Lighting Facts® product label

The LED Lighting Facts program is a voluntary pledge program to verify that LED lighting products are represented correctly in the market. At AFX we are proud to be voluntary members in this program. We take pride in our LED fixtures and the Lighting Facts verification process ensures our product is performance tested and the data listed is accurate.

The label itself provides key information of product performance. It guards against exaggerated claims and ensures confidence in consumer purchases. Performance results in five areas; lumens, efficiency, watts, correlated color temperature (CCT) and color rendering index (CRI) are used to measure against the industry standard for LED testing photometric performance, IES LM-79-2008.

Sponsored by the Department of Energy (DOE) this program was designed for the consumer to assure them that the products they are purchasing perform to their expectations.

For more information on LED Lighting Facts, visit [www.lightingfacts.com](http://www.lightingfacts.com)



### ENERGY STAR®

Through innovation and design, AFX is creating the next generation of energy-efficient fixtures by proving that energy-efficient lighting doesn't have to be uninteresting. As you browse through our catalog look for the ENERGY STAR logo. This identifies ENERGY STAR qualified products throughout this catalog. Consult factory or [www.energystar.gov](http://www.energystar.gov) for current listing.




AFX has dedicated to being environmentally responsible and preserving our natural resources. As a company we continually strive to reduce our carbon footprint and global emissions, not only in the products we sell, but in the materials we use to promote them. Our philosophy of offering products that are technologically advanced as well as energy efficient runs through our company down to our internal recycling program.

Fluorescent lamps contain trace amounts of Mercury. If lamp is marked Hg it contains Mercury and must be disposed of properly. Follow local and/or state laws regarding disposal of fluorescent lamps. Information regarding lamp recycling can be found at [www.epa.gov/cfl](http://www.epa.gov/cfl) or [www.lamprecycle.org](http://www.lamprecycle.org)

## Color Temperature

When selecting bulbs for AFX fixtures, it's important to consider color temperature in relation to the application. Whether for a residence or a commercial space, for a productive environment or leisure area, it's a subjective and personal choice. But, there are some generally accepted standards: Warm light is better for residential living areas; cool light is better for task areas such as the kitchen or office. Current energy-efficient technology allows for a high level of quality across the whole color spectrum, so the choice is yours. The chart below offers some suggestions. Consult your lamp supplier for more specific applications.



## Ballast Troubleshooting

It is important to know which ballast is in the fluorescent fixture and which lamp is compatible with that ballast. Not using the correct lamp may result in ballast overheating, ballast thermal cycling or premature ballast failure. AFX products offer superior ballasting, but it is very important to use the proper lamp for optimum performance. Here are several tips for ballast troubleshooting:

SYMPTOM	CORRECTIVE ACTION
<b>LAMPS WILL NOT OPERATE</b>	<ol style="list-style-type: none"> <li>1. CHECK IF THERE IS POWER TO THE FIXTURE</li> <li>2. BE SURE LAMP IS PROPERLY SEATED IN SOCKET</li> <li>3. REPLACE LAMP</li> <li>4. RESET OR CHANGE STARTER (PREHEAT ONLY)</li> <li>5. CHECK WIRING CONNECTIONS</li> <li>6. TEST BALLAST</li> </ol>
<b>SLOW OR ERRATIC STARTING</b>	<ol style="list-style-type: none"> <li>1. CHECK GROUND (FIXTURE MUST BE GROUNDED FOR RELIABLE STARTING)</li> <li>2. CHECK BALLAST LABEL FOR CORRECT LAMP</li> <li>3. CHECK WIRING CONNECTIONS</li> <li>4. CHECK FOR LOW SUPPLY VOLTAGE</li> <li>5. BE SURE LAMP IS PROPERLY SEATED IN SOCKET</li> <li>6. TEST BALLAST</li> </ol>
<b>EXCESSIVE NOISE</b>	<ol style="list-style-type: none"> <li>1. TIGHTEN LOOSE COMPONENTS</li> <li>2. INSTALL BALLASTS OF THE PROPER SOUND RATING</li> <li>3. REPLACE FAULTY BALLAST(S). NORMAL OPERATION SHOULD RESUME</li> <li>4. NOTE: ALL FLUORESCENT BALLASTS EMIT SOME NOISE</li> </ol>
<b>LAMPS ARE CYCLING</b>	<ol style="list-style-type: none"> <li>1. CHECK AIR TEMPERATURE IN AND AROUND THE FIXTURE</li> <li>2. CHECK BALLAST AND COIL TEMPERATURES - BALLAST CASE TEMPERATURES SHOULD NOT EXCEED 90°C AND COIL TEMPERATURES SHOULD NOT EXCEED 105°C</li> <li>3. REMOVE BUILDING INSULATION FROM ABOVE FIXTURES TO ALLOW FOR HEAT DISSIPATION</li> <li>4. REPLACE FAULTY BALLAST(S). NORMAL OPERATION SHOULD RESUME</li> </ol>
<b>INTERFERENCE</b>	<ol style="list-style-type: none"> <li>1. RADIO AND ANTENNA MUST BE 4 - 10 FEET FROM LAMPS</li> <li>2. CORRECT CONDITION BY USE OF RADIO INTERFERENCE FILTERS</li> <li>3. LIGHTING FIXTURES SHOULD BE ON SEPARATE ELECTRICAL</li> </ol>

## Linear Electronic Ballast and Lamp System Performance

BALLAST TYPE	LAMP DESCRIPTION	VOLTAGE	LAMP WATTS	LAMP SIZE	DESCRIPTION	LIFE HOURS	APPROX. INPUT WATTS	INITIAL DELIVERED LUMENS	THD%	POWER FACTOR	AMPS
R8	RESIDENTIAL ELECTRONIC NORMAL POWER FACTOR 120V		32W	T8	F32T8/TL841	20,000	56	5016	≤ 120	≥ 50	
MV	COMMERCIAL/RESIDENTIAL ELECTRONIC HIGH POWER FACTOR	120V 277V	32W 32W	T8 T8	F32T8/TL841 F32T8/TL841	20,000 24,000	58 56	5016 5251	≤ 30 ≤ 10	≥ 90 ≥ 99	.49 .22
EN	RESIDENTIAL	120V	32W	CFQ	PL-C-4 PIN	12,000	51	3420	≤ 10	≥ 99	.43

## LED Driver System Performance

DRIVER TYPE	DESCRIPTION	INPUT VOLTAGE	OUTPUT CURRENT (mA)	POWER FACTOR	MIN. STARTING TEMP.	DIMMABLE
D1	RESIDENTIAL ELECTRONIC HIGH POWER FACTOR	120V	220-800	>0.90	-30°F/-34°C	YES - TRIAC (FORWARD PHASE OR LEADING-EDGE)/ ELV (REVERSE-PHASE OR TRAILING-EDGE)
MV	COMMERCIAL/RESIDENTIAL ELECTRONIC HIGH POWER FACTOR	120-277V	350-800	>0.90	-30°F/-34°C	NO
UD	COMMERCIAL/RESIDENTIAL ELECTRONIC HIGH POWER FACTOR	120-277V	250-2100	>0.90	-30°F/-34°C	YES - TRIAC (FORWARD PHASE OR LEADING -EDGE)/ ELV (REVERSE-PHASE OR TRAILING-EDGE)
D2	COMMERCIAL ELECTRONIC HIGH POWER FACTOR	120-277V	350-800	>0.90	-30°F/-34°C	AND 0-10V YES - 0-10V

## Lighting Definitions

**BALLAST FACTOR** – Ratio of a lamp’s light output on ballast compared to the lamp’s rated light output. The higher the ballast factor, the more light delivered.

**CIRCLE E BALLAST** – Indicates special EPACT compliant version of ballast. Check the laws and codes for specific applications.

**COLOR TEMPERATURE OR CHROMATICITY** – The appearance of the light that comes from a light source. The color temperature is measured in Kelvin or “K”. The higher the color temperature, the visually cooler or bluer the light appears.

**COLOR RENDERING INDEX** – CRI indicates how true-to-color lighted objects appear. A higher number means truer color. The CRI rates light sources on a scale of 0 to 100. The higher the CRI, the more vibrant or close to natural the colors of objects appear. Light from lamps with good (70-80 CRI) and excellent (80+ CRI) color rendering properties is said to be “high quality light” because objects and people look more appealing, and the light level itself is perceived to be higher.

**ELECTRONIC BALLAST** – A ballast that utilizes electronic components to transform current at high frequency to operate fluorescent or discharge lamps.

**FOOTCANDLE** – The measurement of the amount of light reaching a surface. Footcandles are measured in lumens per square foot.

**LAMP EFFICACY** – Different lamp types have different abilities to convert electrical power (watts) into visible light (lumens). The quantity of light emitted (measured in lumens) is divided by the input power (watts) to determine the lamp’s efficacy. This is expressed as lumens per watt or LPW.

**LED** – The common abbreviation for light-emitting diode. Each individual LED consists of a semiconductor diode that emits light when a voltage is applied to it.

**LIFE** – How long on average a bulb is estimated to last (median life). The number of burning hours on average, after which 50% of large representative groups of lamps in laboratory tests, under controlled burning conditions and at a specified number of burning hours per start have failed.

**LPW** – Lumens per watt is a measure of energy efficiency. Fluorescent lamps are very energy efficient and emit up to 100 lumens per watt.

**LUMENS** – Bulb brightness. A higher number means brighter light. Fluorescent lamp lumens decrease over its life.

**POWER FACTOR** – The ratio of power (watts) to volt-amps of the ballast. The power factor ratio may be used to determine how efficiently total input power is being used. HPF ballasts require less AC current to do an optimum lighting job than would be required by an equivalent low power factor ballast. Additionally, fewer LPF fixtures can be installed in the circuit, increasing installation cost.

**VOLTAGE** – A measurement of electromotive force or the pressure of electricity. Typical residential construction is 120V @ 60Hz Typical commercial construction is 120V or 277V @ 60Hz

**WATTAGE** – A measurement of power.

# Index

## A

AAF.....	145
ABP.....	32
ADS.....	63
ADWW.....	128
AEL.....	224
AGP.....	17
ALB.....	210
ALF.....	161
ALS.....	98
ALV.....	114
ANF.....	157
ANP.....	37
ANS.....	73
APF.....	152
APP.....	34
APS.....	66
ARMF.....	194
ARP.....	24
ARPB.....	24
ARPC.....	24
ARS.....	94
ARV.....	116
ARW.....	196
ATL.....	222
ATLF.....	149, 222
AUW.....	185
AXF.....	72, 151

## B

BBB.....	216
BBF.....	173
BBP.....	46
BBS.....	102
BBV.....	119
BBW.....	199
BEPL.....	31
BESL.....	88
BLW.....	181
BMW.....	183
BNSW.....	200
BOF.....	141
BRS.....	97
BRW.....	192
BWSW.....	203

## C

C2F.....	178
CAC.....	174
CAF.....	174
CARF.....	138
CCM.....	227
CEF.....	171
CES.....	103
CEV.....	117
CEW.....	197
CFE.....	175
CHRF.....	134
CHS.....	51
CHV.....	111
CK4W.....	224
CLL.....	228
CMB.....	215
CMF.....	178
CN.....	227
COS.....	49
CRRF.....	137
CSF.....	178
CSW.....	229, 230
CVF.....	177
CYB.....	208
CZF.....	153
CZP.....	45
CZV.....	112

## D

DIMCONTROL.....	252, 253
DISF.....	131
DYP.....	38

## E

EDF.....	155
EDS.....	67
EL.....	249
ELS.....	74
ENP.....	22
EOV.....	124
ES.....	249
EYELED.....	252

## F

FR68.....	251
FTS.....	57
FUF.....	172
FUS.....	104
FUV.....	120
FUW.....	202

## G

GAF.....	71, 163
GEPL.....	30
GNS.....	78
GRAF.....	133
GZL.....	226

## H

HDB.....	214
HKC.....	223
HKR.....	223
HKS.....	223
HNSW.....	201
HPL.....	223
HPLJN.....	223
HPLJW.....	223
HRP.....	15
HVB.....	206
HZC.....	167

## I

IDB.....	213
IDS.....	99

## K

KAS.....	75
KB12.....	248, 251, 252
KCM.....	227

## L

L01.....	256
L02.....	256
L06.....	256
L07.....	257
L08.....	257
L09.....	257
L13.....	262
L16.....	262
L17.....	262
L22.....	263
L46.....	260
L47.....	260
L49.....	260
L182.....	265
L300.....	258
L302.....	259
L304.....	258
L337.....	258
L500.....	264
L501.....	264
L720.....	263
L721.....	263

LAPL.....	29, 89
LAS.....	105
LASL.....	89
LC.....	228
LCL.....	228
LCS.....	95
LCX.....	238, 245
LED18.....	264
LEDCC.....	252, 253
LGW.....	187
LSL.....	232
LW.....	231
LWL.....	231
LYF.....	70, 162

## M

MAF.....	72, 151
MAR.....	230
MCC.....	226
MCF.....	154
MCM.....	226
MCP.....	43
MIDF.....	164
MIDS.....	92
MNS.....	90
MRF.....	165
MRS.....	100
MTRF.....	136
MXW.....	189

## N

NLF.....	160
NLLP.....	240
NLS.....	87
NLV.....	125
NMS.....	69
NVS.....	61
NVV.....	108
NXL.....	243

## O

OSF.....	159
OSP.....	41
OTP.....	18
OTS.....	64
OTSD.....	64

## P

PCV.....	113
PIDF.....	176
PLB.....	218
PSLED.....	252, 253
PTS.....	59

## R

R55.....	251
RAB.....	207
RAL182.....	265
RC.....	229
REF.....	170
RES.....	93
RHP.....	42
RIS.....	122
RNS.....	53
RNV.....	109
RVF.....	143

## S

S.....	233
SAF.....	156
SAP.....	40
SCC.....	249
SDC.....	249
SEW.....	191
SHB.....	211

SHC.....	166
SHS.....	85
SLB.....	209
SLF.....	147, 221
SLL.....	221
SNF.....	146
SNS.....	68
SNV.....	110
SPC.....	249
SPLE.....	238
SPP.....	13
SR45.....	253
SR68.....	253
SSP.....	21
ST.....	232
STEM.....	224
STICK2.....	248
STICK3.....	248
STICKPS.....	248, 251, 252
STICK/TB.....	251, 252
STN.....	233
SUF.....	150
SXPL.....	27

## T

T5L.....	242
T5U.....	244
T8U.....	244
TAF.....	168
TAS.....	91
TAV.....	118
TBLED/B.....	252
TLD.....	256, 257, 258
TLW.....	256, 257, 258, 259, 265
TPDW.....	204
TRS.....	96
TYS.....	83

## U

UCM.....	227
USS.....	106

## V

V8PN.....	126
VIP.....	21
VNV.....	121
VSC.....	127
VSW.....	127
VTL.....	234

## W

WCM.....	227
WES.....	76
WLF.....	158
WLP.....	36

## X

XLG.....	245
XLH.....	245

## Z

ZOS.....	55
ZUF.....	148, 220
ZUL.....	220

## Photo credits:

Bilbao Outdoor  
Wall Sconce  
Lightology, LLC  
Chicago, IL  
www.lightology.com

Laveer Pendant  
Dundee Library  
East Dundee, IL

Taylor Flush Mount  
Noma Apartment  
Building  
Washington, D.C.  
Whitney Cox  
New York, NY

Brio Outdoor  
Wall Sconce  
LaQuinta Inn  
Arlington Heights, IL  
John Schmuttenmaer

Dayton Pendant  
Time Warner Cable  
Racine, WI  
John Schmuttenmaer

©2017 AFX  
All rights reserved.

Specifications subject to  
change without notice.

Specific items may be  
protected by patents  
or patents pending.









2345 N. Ernie Krueger Circle • Waukegan, IL 60087  
847.249.5970 • [AFXinc.com](http://AFXinc.com)

AFXCR0317