



LIGHTING CATALOG

*Light Fixtures, Ceiling Fans
& Accessories*



Contents



DesignerYou® 6-15

Adjustable Pendant Fixtures	7
Lighting Fixtures	8-9
2¼" Fitter Pendant/Vanity Glass	10-15



Light Fixtures 16-89

Interior Lighting Collections	16-34
Chapel Hill	24
Churchville	31
Clinton	23
Elena I & II	21
Fallon	30
Fontane	30
Gatehouse Tower	26
Hearthstone	26
Kings Canyon	25
Parker Mews	28-29
Regal Springs	33
Spring Valley	32
Swanstone	22
Sylvestre	19
Treebridge Station	27
Trinity I & II	34
Wensley	20
Interior Hanging	35-45
Interior Ceiling	46-61
Interior Wall	62-72
Exterior	73-87
Accent Lighting	
Slimline Picture Lights	88-89



Lamps are not included with product unless otherwise noted. We recommend using Westinghouse lamps in all of our ceiling fans and light fixtures. To help serve you better, Westinghouse Lighting reserves the right to make changes and/or improvements (both visually and technically) to the products in this catalog without notice. As a result, some products and/or product information may change.

Visit our website for the latest specifications.



Ceiling Fans 90-121

Contemporary

Alloy	97
Bendan	93
Arcadia	98
Castle	101
Comet	100
Cumulus	97
Delancey	93
Elite	101
Harmony	99
Lavada	98
Origami	94
Panorama	102
Roundabout	95
Quince	94
Solana	99
Sparta	99
Techno	93
Turbo Swirl	96
Turbo Swirl CFL	96
Vector Elite	101
Wengue	95
Xavier	102
Xavier II	102

Traditional

Bethany	105
Casanova	112
Casanova Supreme	113
Contempra Trio	109
Contempra IV	110-111
Contempra V	111
Fairview	104
Newtown	108
Petite	112
Princess Ambiance	113
Richboro SE	108
Sumter	105
Swirl	106
Vintage	107
Vintage II	107

Indoor/Outdoor

Bayside	116
Brentford	114
Lafayette	115
Oasis	115
Willow Breeze	116

Industrial/Contractor

Contractor's Choice	119
Industrial	118
Industrial 78003	119

Ceiling Fan Specifications	120-121
----------------------------	---------

Ceiling Fan Accessories 122-133

Ceiling Fan Light Kits	123
Extension Down Rods	124
Ceiling Fan Controls	125
Cathedral Ceiling Fan Canopy Kits	126
Pull Chains	127-130
Fan Hardware, Beaded Chain and Accessories	131-133



**Ceiling Fan and Light
Fixture Accessories 134-147**

Recessed Light Converter.....135

Ceiling Medallions

 Medallion Size
 & Installation Guide.....136

 Polyurethane Medallions.....137

 Molded Plastic Medallions.....138

Support Braces & Boxes for
Ceiling Fans & Light Fixtures

 Saf-T-Brace®.....139-141

 Saf-T-Bar®.....142

 Saf-T-Box®.....143

 Sidemount Plus Fan Box®.....144

 Saf-T-Pan®.....145

 Fan Master®, Fan Master Jr.®.....146

 Saf-T-Grid®.....147



**Replacement
Glass and Shades 148-166**

2¼" Fitter Glass.....149-155

Glass Diffusers.....156-157

Chimneys.....158-159

Globes 3¼" & 4" Fitters.....160-161

Polycarbonate & Acrylic Shades.....162

Glass, Polycarbonate & Acrylic Shades...163

Assorted Glass Fitters and Channels....164

Clip-On Shades.....165

Glassware Glossary.....166

Plastic Material Guide.....166



Lighting Hardware 167-198

Glass Shade Holder Kits
& Accessories.....168

Sockets.....169-172

Porcelain Fixture Sockets.....173-177

Switches.....178-179

Crossbars.....180-181

Nipples & All Thread Pipes.....182

Assorted Hardware.....183-185

Canopies.....186-187

Swag Light Kits.....188

Swag Hooks.....189

Lamp Harps.....190-191

Finials, Knobs and Risers.....192-193

Parts and Accessories.....194-195

Plugs.....196

Accessories.....197-198

Index.....199-204

We make lighting choices easy...

From legislation to innovative new products, the selection of the right products can be daunting. At Westinghouse, we make lighting choices easy.

Efficiency and variety define the Westinghouse Lighting products. Our latest products feature technological advances that create a more beautiful, comfortable and energy-efficient space.

Our foundation is based on developing products that will enhance your lifestyle. Generations have trusted Westinghouse to make comfort and convenience a priority. We're continuing that tradition today. Whether you're looking for the latest technology or reliable quality products, we provide lighting choices that guide you in the right direction.

We continuously explore innovative options and new technologies that maximize your lighting experience. Our friendly customer relations team is here to help you find the perfect lighting solution. Call 1-800-999-2226 and speak to one of our team members.

Visit our website www.westinghouselighting.com for the most up-to-date products and specifications.



WESTINGHOUSE

a household name for generations...

George Westinghouse was a renowned inventor long before his name became a brand. He is one of the most productive inventors on record, credited with over 400 patents — many of them “firsts” that changed the way the world lived.

One of Westinghouse’s primary contributions to modern life was his championing of alternating current (AC) rather than the direct current (DC) systems favored by Thomas Edison. Because AC was dramatically safer, Westinghouse’s victory over Edison led to the electrification of American homes. To demonstrate the advantages of AC, Westinghouse staged grand displays like the illumination of the 1893 World’s Fair.

George Westinghouse’s spirit of innovation and commitment to improving quality of life is alive and flourishing at Westinghouse Lighting.

For over 125 years, people all over the world have trusted Westinghouse to provide high quality, reliable products for their homes and businesses. We’re continuing that tradition today with our extensive assortment of light bulbs, lighting fixtures, ceiling fans and accessories. Customers in 128 countries on six continents choose Westinghouse Lighting for quality products and dependable customer service.





DesignerYou®

your light, your choice...


Fully customizable fixtures inspire creativity for quick and easy home upgrades. Pair stylish 2¼" fitter glass with sleek lighting fixtures or transform existing lighting with designer glass shades. It's as easy as 1-2-3.



Choose Your Fixture and Finish.

Pendant Light Fixtures
are adjustable.
Cord Length: 50"

new!



01011 Recessed Light Converter

Transform existing recessed lighting into a pendant or other light fixture!

- Quick and easy home upgrade with no remodeling
- Adjusts to any recessed can size between 4" - 6" diameter
- Works with existing recessed cans that use medium base lamps
- Can be used on sloped ceilings up to 45°
- 50 lb. maximum load rating




85718
**1 Light Adjustable
Mini Pendant**
Chrome Finish


new!



70286
**1 Light Adjustable
Mini Pendant**
White Finish



70287
**1 Light Adjustable
Mini Pendant**
Antique Brass Finish



70284
**1 Light Adjustable
Mini Pendant**
Brushed Nickel Finish



70285
**1 Light Adjustable
Mini Pendant**
Oil Rubbed Bronze Finish

Height: 55" Diameter: 5" Cord Length: 50" Use (1) Medium (E26) Base Lamp, 60 Watt Maximum.



63012
**3 Light Adjustable
Mini Pendant**
Brushed Nickel Finish



63013
**3 Light Adjustable
Mini Pendant**
Oil Rubbed Bronze Finish

Height: 64.63" Length: 23.5" Width: 4.5" Cord Length: 50" Use (3) Medium (E26) Base Lamps, 60 Watt Maximum.

Choose Your Fixture and Finish.



*** 67480**
3 Light Wall with Arm
 Brushed Nickel Finish
 Height: 5.88"
 Width: 22.63"
 Extends: 8.63"

Use (3) Medium (E26) Base Lamps,
 60 Watt Maximum.



*** 67481**
3 Light Wall with Arm
 Oil Rubbed Bronze Finish
 Height: 5.88"
 Width: 22.63"
 Extends: 8.63"

Use (3) Medium (E26) Base Lamps,
 60 Watt Maximum.



*** 67482**
3 Light Wall
 Brushed Nickel Finish
 Height: 5.5"
 Width: 21.13"
 Extends: 5"

Use (3) Medium (E26) Base Lamps,
 60 Watt Maximum.



*** 67485**
3 Light Wall
 Oil Rubbed Bronze Finish
 Height: 5.5"
 Width: 21.13"
 Extends: 5"

Use (3) Medium (E26) Base Lamps,
 60 Watt Maximum.



*** 63006**
3 Light Wall
 Oil Rubbed
 Bronze Finish
 Height: 7"
 Width: 19.5"
 Extends: 6.5"

Use (3) Medium (E26) Base Lamps,
 60 Watt Maximum.



*** 63008**
3 Light Wall
 Brushed
 Nickel Finish
 Height: 7"
 Width: 19.5"
 Extends: 6.5"

Use (3) Medium (E26) Base Lamps,
 60 Watt Maximum.

*** 63018**
3 Light Wall
 Antique Brass Finish
 Height: 7"
 Width: 19.5"
 Extends: 6.5"

Use (3) Medium (E26) Base Lamps,
 60 Watt Maximum.



*Fixture can be installed up or down

Choose Your Fixture and Finish.

*** 63000**
1 Light Wall
*Oil Rubbed
 Bronze Finish*
 Height: 9"
 Width: 4"
 Extends: 6.5"



Use (1) Medium (E26) Base Lamp,
 60 Watt Maximum

*** 63002**
1 Light Wall
*Brushed
 Nickel Finish*
 Height: 9"
 Width: 4"
 Extends: 6.5"



Use (1) Medium (E26) Base Lamp,
 60 Watt Maximum

*** 63005**
2 Light Wall
*Brushed
 Nickel Finish*
 Height: 6.5"
 Width: 11"
 Extends: 5"



Use (2) Medium (E26) Base Lamps,
 60 Watt Maximum.

*** 63003**
2 Light Wall
*Oil Rubbed
 Bronze Finish*
 Height: 6.5"
 Width: 11"
 Extends: 5"



Use (2) Medium (E26) Base Lamps,
 60 Watt Maximum.



*** 63011**
4 Light Wall
Brushed Nickel Finish
 Height: 7"
 Width: 24"
 Extends: 6.5"

Use (4) Medium (E26) Base Lamps,
 60 Watt Maximum.



*** 63009**
4 Light Wall
Oil Rubbed Bronze Finish
 Height: 7"
 Width: 24"
 Extends: 6.5"

Use (4) Medium (E26) Base Lamps,
 60 Watt Maximum.

Choose Your Glass Shade.

2¼" Fitter Glass

2¼" fitter glass is perfect for use with pendant, vanity fixtures, and ceiling fans.

new!



*** 85651**
Imperial Jade Neckless Shade
 Fitter: 2.25"
 Height: 5.88"
 Diameter: 4.88"

new!



*** 85734**
Devonshire Linen Shade
 Fitter: 2.25"
 Height: 6.25"
 Diameter: 4.5"

new!



85702
Brushed Nickel Perforated Metal Neckless Shade
 Fitter: 2.25"
 Height: 6.5"
 Diameter: 4.88"



*** 81412**
Lunar Weave Shade
 Fitter: 2.25"
 Height: 5.88"
 Diameter: 5.38"

new!



*** 85703**
Honeycomb Shade
 Fitter: 2.25"
 Height: 5.88"
 Diameter: 5.25"

new!



*** 85730**
Neckless Fire Pit Long Shade
 Fitter: 2.25"
 Height: 8.5"
 Diameter: 4.5"

new!



*** 81631**
Caramel Swirl Long Neckless Shade
 Fitter: 2.25"
 Height: 8.7"
 Diameter: 4.6"

new!



*** 85724**
Lunar Weave Long Shade
 Fitter: 2.25"
 Height: 7.75"
 Diameter: 4.75"

*Hand blown glass

Choose Your Glass Shade.



*** 85722**
**White Opal
 Fluted Shade**
Fitter: 2.25"
Height: 5.5"
Diameter: 4.75"



*** 81407**
**Garden
 Moss Shade**
Fitter: 2.25"
Height: 5.25"
Diameter: 4.5"

*** 81310**
**Giraffe
 Spot Shade**
Fitter: 2.25"
Height: 5.38"
Diameter: 4.5"



*** 81311**
**Fire
 Pit Shade**
Fitter: 2.25"
Height: 5.38"
Diameter: 4.5"



*** 81409**
**Charcoal
 Swirl Shade**
Fitter: 2.25"
Height: 5.25"
Diameter: 4.85"



*** 81400**
**Wildfire
 Cylinder Shade**
Fitter: 2.25"
Height: 6.5"
Diameter: 4.75"

*** 81404**
**Marble
 Cylinder Shade**
Fitter: 2.25"
Height: 6.5"
Diameter: 4.75"



new!



*** 85723**
**Amber Drum
 Neckless Shade**
Fitter: 2.25"
Height: 5.9"
Diameter: 5.1"




*** 85701**
**Ice
 Cylinder Shade**
Fitter: 2.25"
Height: 6.5"
Diameter: 4.75"

*** 85700**
**Amber Mist
 Cylinder Shade**
Fitter: 2.25"
Height: 6.5"
Diameter: 4.75"



Choose Your Glass Shade.



*** 81410**
Chocolate Drizzle Shade
 Fitter: 2.25"
 Height: 6.38"
 Diameter: 4.38"



*** 81405**
Van Gogh Shade
 Fitter: 2.25"
 Height: 6.25"
 Diameter: 4.38"



*** 81413**
Chili Pepper Shade
 Fitter: 2.25"
 Height: 6.25"
 Diameter: 4.38"



*** 81315**
Clear with Black Rope Shade
 Fitter: 2.25"
 Height: 5.75"
 Diameter: 4.63"



*** 81314**
Clear with White Rope Shade
 Fitter: 2.25"
 Height: 5.75"
 Diameter: 4.63"



*** 81414**
Linen Globe
 Fitter: 2.25"
 Height: 4.88"
 Diameter: 5.25"



*** 81303**
Amber and Brown Shade
 Fitter: 2.25"
 Height: 6.25"
 Diameter: 4.5"



*** 81427**
Spice Swirl Shade
 Fitter: 2.25"
 Height: 5.75"
 Diameter: 4.63"



*** 81364**
Temptress Red Shade
 Fitter: 2.25"
 Height: 5.25"
 Diameter: 4"

*Hand blown glass

Choose Your Glass Shade.

81121
Square
Tiffany Shade
Fitter: 2.25"
Height: 5.13"
Width: 4.75"



81279
Milky
Scavo Bell
Fitter: 2.25"
Height: 5.13"
Diameter: 5.13"



81098
Milky
Scavo Bell
Fitter: 2.25"
Height: 5.25"
Diameter: 5.5"



81257
Sandy
Fluted Bell
Fitter: 2.25"
Height: 4.75"
Diameter: 5.5"



81119
Licorice
Marbleized Bell
Fitter: 2.25"
Height: 4.5"
Diameter: 4.75"



81167
Brown Swirl Bell
Fitter: 2.25"
Height: 5.13"
Diameter: 5.88"



81272
Milky Scavo Bell
Fitter: 2.25"
Height: 4.75"
Diameter: 5.38"



*** 81363**
Burnt Umber Swirl Bell
Fitter: 2.25"
Height: 4.81"
Diameter: 5.38"



81265
Hand-Painted
Leaf Design Bell
Fitter: 2.25"
Height: 4.75"
Diameter: 5.38"



*** 81356**
Tortoise Bell
Fitter: 2.25"
Height: 5.25"
Diameter: 4.75"



*Hand blown glass
www.westinghouselighting.com

Choose Your Glass Shade.



81382
Linen
Pendant Shade
Fitter: 2.25"
Height: 5"
Diameter: 7.75"



81135
Amber Swirl
Pendant Shade
Fitter: 2.25"
Height: 5"
Diameter: 7.75"



*** 81375**
Tortoise
Pendant Shade
Fitter: 2.25"
Height: 5"
Diameter: 7.5"



*** 81353**
Clear and White
Design Bell
Fitter: 2.25"
Height: 4.75"
Diameter: 5"



81422
Brown
Marbleized Bell
Fitter: 2.25"
Height: 4.75"
Diameter: 5.38"



81391
Antique
Smolder Bell
Fitter: 2.25"
Height: 4.75"
Diameter: 5.25"



81120
Cappuccino
Swirl Shade
Fitter: 2.25"
Height: 4.25"
Diameter: 6.88"



81333
Honey Swirl
Scavo Shade
Fitter: 2.25"
Height: 4.38"
Diameter: 6.88"



81365
Parchment
Leaf Shade
Fitter: 2.25"
Height: 4.5"
Diameter: 6"

Choose Your Glass Shade.



81051
Frosted
Etched Bell

Fitter: 2.25"
Height: 4.5"
Diameter: 4.75"



81253
Frosted Bell with
Clear Square Design

Fitter: 2.25"
Height: 4.63"
Diameter: 5.38"



81270
Frosted and Clear
Cross Shade

Fitter: 2.25"
Height: 5.25"
Diameter: 5"



*** 81227**
White
Opal Bell

Fitter: 2.25"
Height: 4.75"
Diameter: 5.12"



*** 81095**
Clear
Seeded Bell

Fitter: 2.25"
Height: 4.62"
Diameter: 5"



81277
Beveled
Clear Bell

Fitter: 2.25"
Height: 4.75"
Diameter: 5.12"



81099
Etched Clear
Shell Bell

Fitter: 2.25"
Height: 5"
Diameter: 4.75"



81072
Frosted and Clear
Stripe Shade

Fitter: 2.25"
Height: 3.75"
Diameter: 4.63"



81411
Satin Etched
Tulip Shade

Fitter: 2.25"
Height: 5"
Diameter: 4.25"



81097
Frosted
Pleated Shade

Fitter: 2.25"
Height: 5"
Diameter: 4.25"

LIGHT FIXTURES

HANGING FIXTURES



A room's centerpiece is often an exquisite chandelier or pendant. From contemporary to traditional, our styles add simple elegance to any room.

CEILING FIXTURES



Make the ordinary extraordinary with our selection of quality ceiling fixtures available in many styles, finishes and sizes.

WALL FIXTURES



Lighting isn't just for ceilings. Wall lighting complements any room and is perfect for bathrooms, dining rooms and hallways.

EXTERIOR FIXTURES



Lighting fixtures outside of a home make a statement of personality and add a finishing touch. Westinghouse's variety of durable finishes and designs can change any home from drab to fab.



All light fixtures in this catalog are Underwriter Laboratories and ETL Listed for safety. All Westinghouse light fixtures are warranted against defects in material and workmanship for a period of five years from their purchase date.



INTERIOR

light fixture collections


Every aspect of a room reflects style. From a dining room to a kitchen bar, or a bedroom corner to a two-story foyer, Westinghouse offers a variety of light fixtures available in collections and styles that are sure to complement any space.



Sylvestre Collection



*** 62278**
1 Light Wall
Brushed Nickel Finish
with Frosted Seeded Glass
Height: 8.25" Width: 4.75"
Extends: 6.25"
Use (1) Medium (E26) Base Lamp,
60 Watt Maximum



*** 62279**
3 Light Wall
Brushed Nickel Finish
with Frosted Seeded Glass
Height: 8.25" Width: 15.75"
Extends: 6.25"
Use (3) Medium (E26) Base Lamps,
60 Watt Maximum



62276
1 Light Flush
Brushed Nickel Finish
with Frosted Seeded Glass
Height: 6.5" Diameter: 11"
Use (1) Medium (E26) Base Lamp,
60 Watt Maximum



62274
5 Light Chandelier
Brushed Nickel Finish
with Frosted Seeded Glass
Height: 18.5" Diameter: 20.63"
Chain: 36" Wire: 120"
Use (5) Medium (E26) Base Lamps,
60 Watt Maximum



62275
3 Light Chandelier
Brushed Nickel Finish
with Frosted Seeded Glass
Height: 17.63" Diameter: 18.25"
Chain: 36" Wire: 120"
Use (3) Medium (E26) Base Lamps,
60 Watt Maximum

*Fixture can be installed up or down
www.westinghouselighting.com

Wensley Collection



*** 62204**

1 Light Wall

Oil Rubbed Bronze Finish with White Alabaster Glass

Height: 7.13" Width: 5.88"

Extends: 8.13"

Use (1) Medium (E26) Base Lamp, 60 Watt Maximum



*** 62205**

2 Light Wall

Oil Rubbed Bronze Finish with White Alabaster Glass

Height: 7.13" Width: 14.25"

Extends: 8.13"

Use (2) Medium (E26) Base Lamps, 60 Watt Maximum



*** 66220**

3 Light Wall

Oil Rubbed Bronze Finish with White Alabaster Glass

Height: 7.13" Width: 23.38"

Extends: 8.13"

Use (3) Medium (E26) Base Lamps, 60 Watt Maximum



66223

2 Light Semi-Flush

Oil Rubbed Bronze Finish with White Alabaster Glass

Height: 6.5" Diameter: 10.13"

Use (2) Medium (E26) Base Lamps, 60 Watt Maximum



62203

1 Light Flush

Oil Rubbed Bronze Finish with White Alabaster Glass

Height: 6" Diameter: 11.25"

Use (1) Medium (E26) Base Lamp, 60 Watt Maximum



62200

3 Light Chandelier

Oil Rubbed Bronze Finish with White Alabaster Glass

Height: 19" Width: 21"

Chain: 36" Wire: 60"

Use (3) Medium (E26) Base Lamps, 60 Watt Maximum



62201

1 Light Pendant

Oil Rubbed Bronze Finish with White Alabaster Glass

Height: 37.25" Diameter: 5.88"

Use (1) Medium (E26) Base Lamp, 60 Watt Maximum

Includes (3) 9.25" long rods.

Install 1, 2, or 3 rods for customized lengths.

*Fixture can be installed up or down

Elena I & II Collections



*** 62227**
1 Light Wall
 Dark Bronze Finish
 with Antique Amber Glass
 Height: 8.63" Width: 6.25"
 Extends: 9"
 Use (1) Medium (E26) Base Lamp,
 60 Watt Maximum



*** 66031**
3 Light Wall
 Dark Bronze Finish
 with Antique Amber Glass
 Height: 8.88" Width: 24"
 Extends: 10.5"
 Use (3) Medium (E26) Base Lamps,
 60 Watt Maximum

new!



*** 62312**
3 Light Wall
 Chrome Finish
 with Honey Swirl Scavo Glass
 Height: 9" Width: 24.75"
 Extends: 11"
 Use (3) Medium (E26) Base Lamps,
 60 Watt Maximum

new!



*** 62311**
2 Light Wall
 Chrome Finish
 with Honey Swirl Scavo Glass
 Height: 9" Width: 15.87"
 Extends: 11"
 Use (2) Medium (E26) Base Lamps,
 60 Watt Maximum



62225
1 Light Flush
 Dark Bronze Finish
 with Antique Amber Glass
 Height: 6.25" Diameter: 11"
 Use (1) Medium (E26) Base Lamp,
 60 Watt Maximum



66028
2 Light Flush
 Dark Bronze Finish
 with Antique Amber Glass
 Height: 6.75" Diameter: 13"
 Use (2) Medium (E26)
 Base Lamps, 60 Watt Maximum

62224
3 Light Chandelier
 Dark Bronze Finish
 with Antique Amber Glass
 Height: 21.25" Width: 19.13"
 Chain: 36" Wire: 120"
 Use (3) Medium (E26)
 Base Lamps, 60 Watt Maximum



62223
5 Light Chandelier
 Dark Bronze Finish
 with Antique Amber Glass
 Height: 25.5" Width: 23.13"
 Chain: 36" Wire: 120"
 Use (5) Medium (E26)
 Base Lamps, 60 Watt Maximum



*Fixture can be installed up or down
www.westinghouselighting.com

Swanstone Collection



*** 62285**
3 Light Wall
 Satin Nickel Finish
 with White Opal Glass
 Height: 8.25" Width: 24.25"
 Extends: 9.38"
 Use (3) Medium (E26) Base Lamps,
 60 Watt Maximum



*** 62284**
1 Light Wall
 Satin Nickel Finish
 with White Opal Glass
 Height: 7.5" Width: 7.13"
 Extends: 9.63"
 Use (1) Medium (E26) Base Lamp,
 60 Watt Maximum



62282
1 Light Flush
 Satin Nickel Finish
 with White Painted Glass
 Height: 6" Diameter: 11.38"
 Use (1) Medium (E26) Base Lamp,
 60 Watt Maximum

62281
3 Light Chandelier
 Satin Nickel Finish
 with White Opal Glass
 Height: 15.13" Diameter: 24"
 Chain: 36" Wire: 60"
 Use (3) Medium (E26)
 Base Lamps,
 60 Watt Maximum



62280
5 Light Chandelier
 Satin Nickel Finish
 with White Opal Glass
 Height: 15.13" Diameter: 24"
 Chain: 36" Wire: 60"
 Use (5) Medium (E26)
 Base Lamps,
 60 Watt Maximum



*Fixture can be installed up or down

Clinton Collection



*** 62272**

1 Light Wall

Satin Nickel Finish
with White Alabaster Glass

Height: 9.25" Width: 5.88"

Extends: 8.38"

Use (1) Medium (E26) Base Lamp,
60 Watt Maximum



*** 62273**

3 Light Wall

Satin Nickel Finish
with White Alabaster Glass

Height: 9.25" Width: 22"

Extends: 8.38"

Use (3) Medium (E26) Base Lamps,
60 Watt Maximum



62270

1 Light Flush

Satin Nickel Finish
with White Alabaster Glass

Height: 5.5" Diameter: 11"

Use (1) Medium (E26) Base Lamp,
60 Watt Maximum



62271

2 Light Flush

Satin Nickel Finish
with White Alabaster Glass

Height: 5.63" Diameter: 13"

Use (2) Medium (E26) Base Lamps,
60 Watt Maximum

62269

3 Light Chandelier

Satin Nickel Finish
with White Alabaster Glass

Height: 21.25" Diameter: 21.5"

Chain: 36" Wire: 120"

Use (3) Medium (E26) Base Lamps,
60 Watt Maximum



62268

5 Light Chandelier

Satin Nickel Finish
with White Alabaster Glass

Height: 22.13" Diameter: 23"

Chain: 36" Wire: 120"

Use (5) Medium (E26) Base Lamps,
60 Watt Maximum



*Fixture can be installed up or down

www.westinghouselighting.com

Chapel Hill Collection



*** 62233**

1 Light Wall

*Oil Rubbed Bronze Finish
with Antique Amber Scavo Glass*

Height: 9.13" Width: 5.13"

Extends: 8.63"

*Use (1) Medium (E26) Base Lamp,
60 Watt Maximum*



*** 62234**

3 Light Wall

*Oil Rubbed Bronze Finish
with Antique Amber Scavo Glass*

Height: 9.13" Width: 18.88"

Extends: 8.63"

*Use (3) Medium (E26) Base Lamps,
60 Watt Maximum*

62231

1 Light Flush

*Oil Rubbed Bronze Finish
with Antique Amber Scavo Glass*

Height: 6.13" Diameter: 11"

*Use (1) Medium (E26) Base Lamp,
60 Watt Maximum*



62229

5 Light Chandelier

*Oil Rubbed Bronze Finish
with Antique Amber Scavo Glass*

Height: 18.88" Width: 23.63"

Chain: 36" Wire: 120"

*Use (5) Medium (E26) Base Lamps,
60 Watt Maximum*

62230

3 Light Chandelier

*Oil Rubbed Bronze Finish
with Antique Amber Scavo Glass*

Height: 18.5" Width: 21.75"

Chain: 36" Wire: 120"

*Use (3) Medium (E26)
Base Lamps, 60 Watt Maximum*



*Fixture can be installed up or down

Kings Canyon Collection



* 62220

1 Light Wall

*Oil Rubbed Bronze Finish
with Burnt Scavo Glass*

Height: 9.13" Width: 7"

Extends: 9"

*Use (1) Medium (E26) Base Lamp,
60 Watt Maximum*



* 62221

2 Light Wall

*Oil Rubbed Bronze Finish
with Burnt Scavo Glass*

Height: 9.13" Width: 17"

Extends: 9"

*Use (2) Medium (E26) Base Lamps,
60 Watt Maximum*



* 62222

3 Light Wall

*Oil Rubbed Bronze Finish
with Burnt Scavo Glass*

Height: 9.13" Width: 25"

Extends: 9"

*Use (3) Medium (E26) Base Lamps,
60 Watt Maximum*

62219

2 Light Flush

*Oil Rubbed Bronze Finish
with Burnt Scavo Glass*

Height: 7.25" Diameter: 13.25"

*Use (2) Medium (E26) Base Lamps,
60 Watt Maximum*



62217

1 Light Pendant


*Oil Rubbed Bronze Finish
with Burnt Scavo Glass*

Height: 38.5" Diameter: 7"

*Use (1) Medium (E26) Base Lamp,
60 Watt Maximum*

Includes (3) 9.25" long rods.

*Install 1, 2, or 3 rods for
customized lengths.*



62215

3 Light Chandelier

*Oil Rubbed Bronze Finish
with Burnt Scavo Glass*

Height: 20.13" Diameter: 22.13"

Chain: 36" Wire: 60"

*Use (3) Medium (E26) Base Lamps,
60 Watt Maximum*



62214

5 Light Chandelier

*Oil Rubbed Bronze Finish
with Burnt Scavo Glass*

Height: 23.38" Diameter: 26"

Chain: 36" Wire: 60"

*Use (5) Medium (E26) Base Lamps,
60 Watt Maximum*



*Fixture can be installed up or down

www.westinghouselighting.com

Gatehouse Tower Collection



62252

3 Light Chandelier

Weathered Bronze Finish with Frosted Glass

Height: 18.88" Width: 22.88"

Chain: 36" Wire: 60"

Use (3) Medium (E26) Base Lamps, 60 Watt Maximum

Hearthstone Collection



69001

5 Light Chandelier

Burnished Bronze Patina Finish with Burnt Scavo Glass

Height: 26" Width: 23.5"

Chain: 108" Wire: 120"

Use (5) Medium (E26)

Base Lamps, 60 Watt Maximum



69000

3 Light Chandelier

Burnished Bronze Patina Finish with Burnt Scavo Glass

Height: 21.5" Width: 19"

Chain: 108" Wire: 120"

Use (3) Medium (E26)

Base Lamps, 60 Watt Maximum



69006

1 Light Mini Pendant

Burnished Bronze Patina Finish with Burnt Scavo Glass

Height: 41.25" Diameter: 5"

Use (1) Medium (E26) Base Lamp,

60 Watt Maximum

Includes (3) 9.25" long rods.

Install 1, 2, or 3 rods for customized lengths.



69009

3 Light Wall

Burnished Bronze Patina Finish with Burnt Scavo Glass

Height: 10.75" Width: 19.5

Extends: 8"

Use (3) Medium (E26) Base Lamps,

60 Watt Maximum

*Fixture can be installed up or down

Treebridge Station Collection



62244

2 Light Flush

*Espresso Finish
with White Alabaster Glass*

Height: 5.63" Diameter: 13.5"

*Use (2) Medium (E26) Base Lamps,
60 Watt Maximum*



*** 62245**

1 Light Wall

*Espresso Finish
with White Alabaster Glass*

Height: 10.5" Width: 5"

Extends: 7.5"

*Use (1) Medium (E26) Base Lamp,
60 Watt Maximum*



*** 62247**

3 Light Wall

*Espresso Finish
with White Alabaster Glass*

Height: 10.5" Width: 21.25"

Extends: 7.5"

*Use (3) Medium (E26) Base Lamps,
60 Watt Maximum*

62240

5 Light Chandelier

*Espresso Finish
with White Alabaster Glass*

Height: 24.25" Width: 24.38"

Chain: 36" Wire: 60"

*Use (5) Medium (E26) Base Lamps,
60 Watt Maximum*



***Fixture can be installed up or down**
www.westinghouselighting.com

Parker Mews Collection

*** 62260**

1 Light Wall

*Brushed Nickel Finish
with White Linen Fabric Shade*

Height: 9.75" Width: 5.5"

Extends: 7"

*Use (1) Candelabra (E12) Base Lamp,
60 Watt Maximum*



*** 62261**


2 Light Wall

*Brushed Nickel Finish
with White Linen Fabric Shades*

Height: 9.75" Width: 16"

Extends: 7"

*Use (2) Candelabra (E12) Base Lamps,
60 Watt Maximum*



*** 62262**

3 Light Wall

*Brushed Nickel Finish
with White Linen Fabric Shades*

Height: 9.75" Width: 24"

Extends: 7"

*Use (3) Candelabra (E12) Base Lamps,
60 Watt Maximum*



62258

1 Light Flush

*Brushed Nickel Finish
with White Linen Fabric Shade*

Height: 5.38" Diameter: 11"

*Use (1) Medium (E26) Base Lamp,
60 Watt Maximum*



62259

2 Light Flush

*Brushed Nickel Finish
with White Linen Fabric Shade*

Height: 6" Diameter: 13"

*Use (2) Medium (E26) Base Lamps,
60 Watt Maximum*



62257

2 Light Semi-Flush

*Brushed Nickel Finish
with White Linen Fabric Shade*

Height: 10.75" Width: 13"

*Use (2) Medium (E26) Base Lamps,
60 Watt Maximum*

***Fixture can be installed up or down**



62256


1 Light Pendant

*Brushed Nickel Finish
with White Linen Fabric Shade*

Height: 43.5" Diameter: 5.5"

*Use (1) Candelabra (E12) Base Lamp,
60 Watt Maximum*

*Includes (3) 9.25" long rods.
Install 1, 2, or 3 rods for
customized lengths.*



+ 62254

5 Light Chandelier

*Brushed Nickel Finish
with White Linen Fabric Shades*

Height: 23.13" Width: 25"

Chain: 36" Wire: 60"

*Use (5) Candelabra (E12) Base Lamps,
60 Watt Maximum*

+ 62255

3 Light Chandelier

*Brushed Nickel Finish
with White Linen Fabric Shades*

Height: 23.13" Width: 23.38"

Chain: 36" Wire: 60"

*Use (3) Candelabra (E12) Base Lamps,
60 Watt Maximum*

Fontane Collection



*** 62267**
1 Light Wall
 Brushed Nickel Finish
 with Frosted Glass
 Height: 8.63" Width: 6.5"
 Extends: 7.88"
 Use (1) Medium (E26) Base Lamp,
 60 Watt Maximum



62266
3 Light Pendant
 Brushed Nickel Finish
 with Frosted Glass
 Height: 25.88" Diameter: 19.75"
 Chain: 36" Wire: 60"
 Use (3) Medium (E26) Base Lamps,
 60 Watt Maximum

62265
3 Light Chandelier
 Brushed Nickel Finish
 with Frosted Glass
 Height: 21" Diameter: 21.75"
 Chain: 36" Wire: 60"
 Use (3) Medium (E26) Base Lamps,
 60 Watt Maximum



62264
6 Light Chandelier
 Brushed Nickel Finish
 with Frosted Glass
 Height: 22.5" Diameter: 30.13"
 Chain: 36" Wire: 60"
 Use (6) Medium (E26) Base Lamps,
 60 Watt Maximum

Fallon Collection



62287
2 Light Semi-Flush
 Satin Platinum Finish
 with White Alabaster Glass
 Height: 7.13" Diameter: 13.13"
 Use (2) Medium (E26) Base Lamps,
 60 Watt Maximum



*** 62288**
3 Light Wall
 Satin Platinum Finish
 with White Alabaster Glass
 Height: 7.25" Width: 27.75"
 Extends: 10.5"
 Use (3) Medium (E26) Base Lamps,
 60 Watt Maximum



62286
5 Light Chandelier
 Satin Platinum Finish
 with White Alabaster Glass
 Height: 21.75" Width: 30.5"
 Chain: 36" Wire: 60"
 Use (5) Medium (E26) Base Lamps,
 60 Watt Maximum

*Fixture can be installed up or down



66646

2 Light Flush

*Brushed Nickel Finish with
Frosted White Alabaster Glass
Height: 6.13" Diameter: 13.25"
Use (2) Medium (E26) Base Lamps,
60 Watt Maximum*



66645

3 Light Flush

*Brushed Nickel Finish with
Frosted White Alabaster Glass
Height: 7.38" Diameter: 15"
Use (3) Medium (E26) Base Lamps,
60 Watt Maximum*



*** 66649**

3 Light Wall

*Brushed Nickel Finish with
Frosted White Alabaster Glass
Height: 7.5" Width: 25"
Extends: 8.5"
Use (3) Medium (E26) Base Lamps,
100 Watt Maximum*

66640

3 Light Chandelier

*Brushed Nickel Finish with
Frosted White Alabaster Glass
Height: 17.38" Width: 19.5"
Chain: 108" Wire: 120"
Use (3) Medium (E26) Base Lamps,
60 Watt Maximum*



*** 66647**

1 Light Wall

*Brushed Nickel Finish with
Frosted White Alabaster Glass
Height: 8" Width: 7"
Extends: 8"
Use (1) Medium (E26) Base Lamp,
100 Watt Maximum*



Spring Valley Collection



66590
1 Light Mini Pendant
 Ebony Bronze Finish
 with Aged Alabaster Glass
 Height: 40.5" Diameter: 7"
 Use (1) Medium (E26) Base Lamp,
 100 Watt Maximum
 Includes (3) 9.25" long rods.
 Install 1, 2, or 3 rods for
 customized lengths.



66587
3 Light Chandelier
 Ebony Bronze Finish
 with Aged Alabaster Glass
 Height: 18.38" Width: 21.5"
 Chain: 108" Wire: 120"
 Use (3) Medium (E26) Base Lamps,
 60 Watt Maximum



66584
5 Light Chandelier
 Ebony Bronze Finish
 with Aged Alabaster Glass
 Height: 20" Width: 25"
 Chain: 108" Wire: 120"
 Use (5) Medium (E26) Base Lamps,
 60 Watt Maximum

*** 66596**
3 Light Wall
 Ebony Bronze Finish
 with Aged Alabaster Glass
 Height: 9.5" Width: 25"
 Extends: 8.25"
 Use (3) Medium (E26) Base Lamps,
 100 Watt Maximum



*** 66592**
1 Light Wall
 Ebony Bronze Finish
 with Aged Alabaster Glass
 Height: 9.25" Width: 7"
 Extends: 8"
 Use (1) Medium (E26) Base Lamp,
 100 Watt Maximum



*** 66593**
2 Light Wall
 Ebony Bronze Finish
 with Aged Alabaster Glass
 Height: 9.5" Width: 16"
 Extends: 8"
 Use (2) Medium (E26) Base Lamps,
 100 Watt Maximum



66599
2 Light Flush
 Ebony Bronze Finish
 with Aged Alabaster Glass
 Height: 6" Diameter: 13"
 Use (2) Medium (E26) Base Lamps,
 60 Watt Maximum



*Fixture can be installed up or down

Regal Springs Collection



62209

1 Light Pendant

Ebony Gold Finish with Burnt Scavo Glass
 Height: 41.25" Diameter: 7"
 Use (1) Medium (E26) Base Lamp, 60 Watt Maximum
 Includes (3) 9.25" long rods.
 Install 1, 2, or 3 rods for customized lengths.



*** 62212**

1 Light Wall

Ebony Gold Finish with Burnt Scavo Glass
 Height: 9.5" Width: 7"
 Extends: 9"
 Use (1) Medium (E26) Base Lamp, 60 Watt Maximum



*** 62213**

3 Light Wall

Ebony Gold Finish with Burnt Scavo Glass
 Height: 9.5" Width: 25.25"
 Extends: 9"
 Use (3) Medium (E26) Base Lamps, 60 Watt Maximum



62211

2 Light Flush

Ebony Gold Finish with Burnt Scavo Glass
 Height: 7.5" Diameter: 13.75"
 Use (2) Medium (E26) Base Lamps, 60 Watt Maximum



62210

2 Light Semi-Flush

Ebony Gold Finish with Burnt Scavo Glass
 Height: 12.5" Width: 13"
 Use (2) Medium (E26) Base Lamps, 60 Watt Maximum



62208

3 Light Pendant

Ebony Gold Finish with Burnt Scavo Glass
 Height: 23.5" Width: 19"
 Chain: 36" Wire: 60"
 Use (3) Medium (E26) Base Lamps, 60 Watt Maximum



62207

3 Light Chandelier

Ebony Gold Finish with Burnt Scavo Glass
 Height: 18.25" Width: 19"
 Chain: 36" Wire: 60"
 Use (3) Medium (E26) Base Lamps, 60 Watt Maximum



62206

5 Light Chandelier

Ebony Gold Finish with Burnt Scavo Glass
 Height: 24.5" Width: 25.5"
 Chain: 36" Wire: 60"
 Use (5) Medium (E26) Base Lamps, 60 Watt Maximum

*Fixture can be installed up or down
www.westinghouselighting.com

Trinity I & II Collections

*** 62238**

1 Light Wall

*Oil Rubbed Bronze Finish
with Aged Alabaster Glass*

*Height: 9" Width: 5.13"
Extends: 8"*

*Use (1) Medium (E26) Base Lamp,
60 Watt Maximum*



*** 62239**

3 Light Wall

*Oil Rubbed Bronze Finish
with Aged Alabaster Glass*

*Height: 8.5" Width: 17.25"
Extends: 8.38"*

*Use (3) Medium (E26) Base Lamps,
60 Watt Maximum*



62236

1 Light Flush

*Oil Rubbed Bronze Finish
with Aged Alabaster Glass*

Height: 5.88" Diameter: 11.25"

*Use (1) Medium (E26) Base Lamp,
60 Watt Maximum*



62237

2 Light Flush

*Oil Rubbed Bronze Finish
with Aged Alabaster Glass*

Height: 6.63" Diameter: 13.13"

*Use (2) Medium (E26) Base Lamps,
60 Watt Maximum*

62235

5 Light Chandelier

*Oil Rubbed Bronze Finish
with Aged Alabaster Glass*

*Height: 11" Width: 23"
Chain: 36" Wire: 60"*

*Use (5) Medium (E26) Base Lamps,
60 Watt Maximum*



66008

5 Light Chandelier

*Brushed Nickel Finish
with White Opal Glass*

*Height: 11" Width: 23"
Chain: 36" Wire: 120"*

*Use (5) Medium (E26) Base Lamps,
60 Watt Maximum*



64615

3 Light Chandelier

*Brushed Nickel Finish
with White Opal Glass*

*Height: 12.5" Width: 22"
Chain: 36" Wire: 120"*

*Use (3) Medium (E26) Base Lamps,
60 Watt Maximum*

*Fixture can be installed up or down

HANGING

interior light fixture assortment

Every aspect of a room reflects style. From an elegant dining room to a kitchen bar, or a bedroom corner to two-story entry, Westinghouse offers a variety of hanging fixtures sure to complement any space.





62200
Wensley
3 Light Chandelier
*Oil Rubbed Bronze Finish
 with White Alabaster Glass*
 Height: 19" Width: 21"
 Chain: 36" Wire: 60"
 Use (3) Medium (E26) Base Lamps,
 60 Watt Maximum



62215
Kings Canyon
3 Light Chandelier
*Oil Rubbed Bronze Finish
 with Burnt Scavo Glass*
 Height: 20.13" Diameter: 22.13"
 Chain: 36" Wire: 60"
 Use (3) Medium (E26) Base Lamps,
 60 Watt Maximum



62214
Kings Canyon
5 Light Chandelier
*Oil Rubbed Bronze Finish
 with Burnt Scavo Glass*
 Height: 23.38" Diameter: 26"
 Chain: 36" Wire: 60"
 Use (5) Medium (E26) Base Lamps,
 60 Watt Maximum

66295

5 Light Chandelier
*Weathered Bronze Finish
 with Beige Shades*
 Height: 24.25" Width: 27.63"
 Chain: 36" Wire: 60"
 Use (5) Candelabra (E12) Base Lamps,
 60 Watt Maximum



62240
Treebridge Station
5 Light Chandelier
*Espresso Finish
 with White Alabaster Glass*
 Height: 24.25" Width: 24.38"
 Chain: 36" Wire: 60"
 Use (5) Medium (E26) Base Lamps,
 60 Watt Maximum



62206
Regal Springs
5 Light Chandelier

*Ebony Gold Finish
 with Burnt Scavo Glass
 Height: 24.5" Width: 25.5"
 Chain: 36" Wire: 60"
 Use (5) Medium (E26) Base Lamps,
 60 Watt Maximum*



62207
Regal Springs
3 Light Chandelier

*Ebony Gold Finish
 with Burnt Scavo Glass
 Height: 18.25" Width: 19"
 Chain: 36" Wire: 60"
 Use (3) Medium (E26) Base Lamps,
 60 Watt Maximum*



62224
Elena
3 Light Chandelier

*Dark Bronze Finish
 with Antique Amber Glass
 Height: 21.25" Width: 19.13"
 Chain: 36" Wire: 120"
 Use (3) Medium (E26) Base Lamps,
 60 Watt Maximum*



62223
Elena
5 Light Chandelier

*Dark Bronze Finish
 with Antique Amber Glass
 Height: 25.5" Width: 23.13"
 Chain: 36" Wire: 120"
 Use (5) Medium (E26) Base Lamps,
 60 Watt Maximum*



62229
Chapel Hill
5 Light Chandelier

*Oil Rubbed Bronze Finish
 with Antique Amber Scavo Glass
 Height: 18.88" Width: 23.63"
 Chain: 36" Wire: 120"
 Use (5) Medium (E26) Base Lamps,
 60 Watt Maximum*



62230
Chapel Hill
3 Light Chandelier

*Oil Rubbed Bronze Finish
 with Antique Amber Scavo Glass
 Height: 18.5" Width: 21.75"
 Chain: 36" Wire: 120"
 Use (3) Medium (E26) Base Lamps,
 60 Watt Maximum*



62280

Swanstone

5 Light Chandelier

*Satin Nickel Finish
with White Opal Glass*

Height: 15.13" Diameter: 24"

Chain: 36" Wire: 60"

*Use (5) Medium (E26) Base Lamps,
60 Watt Maximum*



62281

Swanstone

3 Light Chandelier

*Satin Nickel Finish
with White Opal Glass*

Height: 15.13" Diameter: 24"

Chain: 36" Wire: 60"

*Use (3) Medium (E26) Base Lamps,
60 Watt Maximum*



62268

Clinton

5 Light Chandelier

*Satin Nickel Finish
with White Alabaster Glass*

Height: 22.13" Diameter: 23"

Chain: 36" Wire: 120"

*Use (5) Medium (E26) Base Lamps,
60 Watt Maximum*



62269

Clinton

3 Light Chandelier

*Satin Nickel Finish
with White Alabaster Glass*

Height: 21.25" Diameter: 21.5"

Chain: 36" Wire: 120"

*Use (3) Medium (E26) Base Lamps,
60 Watt Maximum*



62264

Fontane

6 Light Chandelier

*Brushed Nickel Finish
with Frosted Glass*

Height: 22.5" Diameter: 30.13"

Chain: 36" Wire: 60"

*Use (6) Medium (E26) Base Lamps,
60 Watt Maximum*



62265

Fontane

3 Light Chandelier

*Brushed Nickel Finish
with Frosted Glass*

Height: 21" Diameter: 21.75"

Chain: 36" Wire: 60"

*Use (3) Medium (E26) Base Lamps,
60 Watt Maximum*



62274

Sylvestre


5 Light Chandelier

*Brushed Nickel Finish
with Frosted Seeded Glass*

Height: 18.5" Diameter: 20.63"

Chain: 36" Wire: 120"

*Use (5) Medium (E26) Base Lamps,
60 Watt Maximum*



62275

Sylvestre

3 Light Chandelier

*Brushed Nickel Finish
with Frosted Seeded Glass*

Height: 17.63" Diameter: 18.25"

Chain: 36" Wire: 120"

*Use (3) Medium (E26) Base Lamps,
60 Watt Maximum*



62252

Gatehouse Tower

3 Light Chandelier

*Weathered Bronze Finish
with Frosted Glass*

Height: 18.88" Width: 22.88"

Chain: 36" Wire: 60"

*Use (3) Medium (E26) Base Lamps,
60 Watt Maximum*



+ 62254

Parker Mews


5 Light Chandelier

*Brushed Nickel Finish
with White Linen Fabric Shades*

Height: 23.13" Width: 25"

Chain: 36" Wire: 60"

*Use (5) Candelabra (E12) Base Lamps,
60 Watt Maximum*



+ 62255

Parker Mews

3 Light Chandelier

*Brushed Nickel Finish
with White Linen Fabric Shades*

Height: 23.13" Width: 23.38"

Chain: 36" Wire: 60"

*Use (3) Candelabra (E12) Base Lamps,
60 Watt Maximum*



+Fixture can be Semi-Flush or Chandelier mounted
www.westinghouselighting.com

66587
Spring Valley
3 Light Chandelier
 Ebony Bronze Finish
 with Aged Alabaster Glass
 Height: 18.38" Width: 21.5"
 Chain: 108" Wire: 120"
 Use (3) Medium (E26) Base Lamps,
 60 Watt Maximum



66584
Spring Valley
5 Light Chandelier
 Ebony Bronze Finish
 with Aged Alabaster Glass
 Height: 20" Width: 25"
 Chain: 108" Wire: 120"
 Use (5) Medium (E26) Base Lamps,
 60 Watt Maximum



69001
Hearthstone
5 Light Chandelier
 Burnished Bronze Patina Finish
 with Burnt Scavo Glass
 Height: 26" Width: 23.5"
 Chain: 108" Wire: 120"
 Use (5) Medium (E26) Base Lamps,
 60 Watt Maximum



69000
Hearthstone
3 Light Chandelier
 Burnished Bronze Patina Finish
 with Burnt Scavo Glass
 Height: 21.5" Width: 19"
 Chain: 108" Wire: 120"
 Use (3) Medium (E26) Base Lamps,
 60 Watt Maximum



66054
5 Light Chandelier
 Polished Brass Finish
 with Clear Ribbed Glass
 Height: 13.75" Width: 23.38"
 Chain: 36" Wire: 120"
 Use (5) Medium (E26) Base Lamps,
 60 Watt Maximum



67141
5 Light Chandelier
 Sienna Finish
 with Frosted Ribbed Glass
 Height: 13.75" Width: 23.38"
 Chain: 36" Wire: 120"
 Use (5) Medium (E26) Base Lamps,
 60 Watt Maximum



66008

Trinity I

5 Light Chandelier

*Brushed Nickel Finish
with White Opal Glass*

Height: 11" Width: 23"

Chain: 36" Wire: 120"

*Use (5) Medium (E26) Base Lamps,
60 Watt Maximum*



62235

Trinity II

5 Light Chandelier

*Oil Rubbed Bronze Finish
with Aged Alabaster Glass*

Height: 11" Width: 23"

Chain: 36" Wire: 120"

*Use (5) Medium (E26) Base Lamps,
60 Watt Maximum*



64615


Trinity I

3 Light Chandelier

Brushed Nickel Finish with White Opal Glass

Height: 12.5" Width: 22" Chain: 36" Wire: 120"

*Use (3) Medium (E26) Base Lamps,
60 Watt Maximum*



69222

Winchester

3 Light Island Pendant

*Brushed Nickel Finish
with Frosted White Alabaster Glass*

Height: 14.75" Width: 37.75"

Chain: 108" Wire: 120" Extends: 11.25"

*Use (3) Medium (E26) Base Lamps,
100 Watt Maximum*



62286

Fontane

5 Light Chandelier

*Satin Platinum Finish
with White Alabaster Glass*

Height: 21.75" Width: 30.5"

Chain: 36" Wire: 60"

*Use (5) Medium (E26) Base Lamps,
60 Watt Maximum*

66640

Churchville

3 Light Chandelier

*Brushed Nickel Finish with
Frosted White Alabaster Glass*

Height: 17.38" Width: 19.5"

Chain: 108" Wire: 120"

*Use (3) Medium (E26) Base Lamps,
60 Watt Maximum*



66088
10 Light Williamsburg Style Chandelier

Polished Brass Finish
 Height: 20" Width: 23.25"
 Chain: 36" Wire: 120"
 Use (10) Candelabra (E12) Base Lamps,
 60 Watt Maximum



66098
5 Light Chandelier

Polished Brass Finish
 Height: 16" Width: 18"
 Chain: 36" Wire: 120"
 Use (5) Candelabra (E12) Base Lamps,
 60 Watt Maximum

66244
1 Light Pendant

*Polished Brass Finish
 with Crystal Ribbed Glass*
 Height: 6" Diameter: 10"
 Cord Length: 48"
 Use (1) Medium (E26) Base Lamp,
 100 Watt Maximum



66198
1 Light Pendant

White Finish
 Height: 8.5" Diameter: 15.5"
 Cord Length: 48"
 Use (1) Medium (E26) Base Lamp,
 100 Watt Maximum



67143
1 Light Pendant

*Sienna Finish
 with Frosted Ribbed Glass*
 Height: 9" Diameter: 16.5"
 Chain: 36" Wire: 120"
 Use (1) Medium (E26) Base Lamp,
 100 Watt Maximum






62208
Regal Springs
3 Light Pendant
 Ebony Gold Finish
 with Burnt Scavo Glass
 Height: 23.5" Width: 19"
 Chain: 36" Wire: 60"
 Use (3) Medium (E26) Base Lamps,
 60 Watt Maximum




62266
Fontane
3 Light Pendant
 Brushed Nickel Finish
 with Frosted Glass
 Height: 25.88" Diameter: 19.75"
 Chain: 36" Wire: 60"
 Use (3) Medium (E26) Base Lamps,
 60 Watt Maximum



66296
3 Light Pendant
 Oil Rubbed Bronze Finish
 with Amber Glass
 Height: 19.13" Width: 15.63"
 Chain: 36" Wire: 60"
 Use (3) Medium (E26) Base Lamps,
 60 Watt Maximum



new!




01011
Recessed Light Converter

Transform existing recessed lighting into a pendant or other light fixture!

- Quick and easy home upgrade with no remodeling
- Unique patent pending design
- Adjusts to any recessed can size between 4" - 6" diameter
- No visible screws or hardware
- Perfect for hanging a pendant or other lighting fixtures
- Decorative medallion can be painted to match any decor
- Works with existing recessed cans that use medium base lamps*
- Can be used on sloped ceilings up to 45°
- 50 lb. maximum load rating

*Converter works with existing recessed cans that use medium base PAR16, R16, A19, R20, PAR20, BR25, BR30, R30, PAR30, BR38, PAR38, BR40 or R40 lamps.



Note: Paintable decorative medallion and metal plate are optional when used on a 4" diameter recessed can.

66590

Spring Valley

1 Light Mini Pendant

*Ebony Bronze Finish
with Aged Alabaster Glass*

Height: 40.5" Diameter: 7"

Use (1) Medium (E26) Base Lamp,

100 Watt Maximum

Includes (3) 9.25" long rods.

*Install 1, 2, or 3 rods for
customized lengths.*



69006

Hearthstone

1 Light Mini Pendant

*Burnished Bronze Patina Finish
with Burnt Scavo Glass*

Height: 41.25" Diameter: 5"

Use (1) Medium (E26) Base Lamp,

60 Watt Maximum

Includes (3) 9.25" long rods.

*Install 1, 2, or 3 rods for
customized lengths.*



62201

Wensley

1 Light Mini Pendant

*Oil Rubbed Bronze Finish
with White Alabaster Glass*

Height: 37.25" Diameter: 5.88"

Use (1) Medium (E26) Base Lamp,

60 Watt Maximum

Includes (3) 9.25" long rods.

*Install 1, 2, or 3 rods for
customized lengths.*



62209

Regal Springs

1 Light Mini Pendant

*Ebony Gold Finish
with Burnt Scavo Glass*

Height: 41.25" Diameter: 7"

Use (1) Medium (E26) Base Lamp,

60 Watt Maximum

Includes (3) 9.25" long rods.

*Install 1, 2, or 3 rods for
customized lengths.*

62217

Kings Canyon

1 Light Mini Pendant

*Oil Rubbed Bronze Finish
with Burnt Scavo Glass*

Height: 38.5" Diameter: 7"

Use (1) Medium (E26) Base Lamp,

60 Watt Maximum

Includes (3) 9.25" long rods.

*Install 1, 2, or 3 rods for
customized lengths.*



*** 67384**

1 Light Mini Pendant

*Oil Rubbed Bronze Finish
with Fire Storm Glass Shade*

Height: 59.5" Diameter: 5"

Cord Length: 50"

*Use (1) Medium (E26) Base Lamp,
60 Watt Maximum*



64532

1 Light Mini Pendant

*Gun Metal Finish
with Perforated Metal Shade*

Height: 56.5" Diameter: 5"

Cord Length: 50"

*Use (1) Medium (E26) Base Lamp,
60 Watt Maximum*



69231

Winchester

1 Light Mini Pendant

*Brushed Nickel Finish
with Frosted White Alabaster Glass*

Height: 38" Diameter: 9.5"

Use (1) Medium (E26) Base Lamp,

100 Watt Maximum

Includes (3) 9.25" long rods.

*Install 1, 2, or 3 rods for
customized lengths.*



67017

Abington

1 Light Mini Pendant

*Weathered Bronze Finish
with Frosted Glass*

Height: 34.25" Diameter: 7.25"

Use (1) Candelabra (E12) Base Lamp,

60 Watt Maximum

Includes (3) 9.25" long rods.

*Install 1, 2, or 3 rods for
customized lengths.*



62256

Parker Mews

1 Light Mini Pendant

*Brushed Nickel Finish
with White Linen Fabric Shade*

Height: 43.5" Diameter: 5.5"

Use (1) Candelabra (E12) Base Lamp,

60 Watt Maximum

Includes (3) 9.25" long rods.

*Install 1, 2, or 3 rods for
customized lengths.*

***Hand Blown Glass**

www.westinghouselighting.com



CEILING

interior light fixture assortment

Inspiration guides our ceiling fixture designs and we offer a wide range of styles and finishes to fit any décor.





62257
Parker Mews
2 Light Semi-Flush
 Brushed Nickel Finish
 with White Linen Fabric Shade
 Height: 10.75" Width: 13"
 Use (2) Medium (E26) Base Lamps,
 60 Watt Maximum



62259
Parker Mews
2 Light Flush
 Brushed Nickel Finish
 with White Linen Fabric Shade
 Height: 6" Diameter: 13"
 Use (2) Medium (E26) Base Lamps,
 60 Watt Maximum



62258
Parker Mews
1 Light Flush
 Brushed Nickel Finish
 with White Linen Fabric Shade
 Height: 5.38" Diameter: 11"
 Use (1) Medium (E26) Base Lamp,
 60 Watt Maximum



62276
Sylvestre
1 Light Flush
 Brushed Nickel Finish
 with Frosted Seeded Glass
 Height: 6.5" Diameter: 11"
 Use (1) Medium (E26) Base Lamp,
 60 Watt Maximum



62282
Swanstone
1 Light Flush
 Satin Nickel Finish
 with White Painted Glass
 Height: 6" Diameter: 11.38"
 Use (1) Medium (E26) Base Lamp,
 60 Watt Maximum



62287
Fallon
2 Light Semi-Flush
 Satin Platinum Finish
 with White Alabaster Glass
 Height: 7.13" Diameter: 13.13"
 Use (2) Medium (E26) Base Lamps,
 60 Watt Maximum



62270
Clinton
1 Light Flush
 Satin Nickel Finish
 with White Alabaster Glass
 Height: 5.5" Diameter: 11"
 Use (1) Medium (E26) Base Lamp,
 60 Watt Maximum



62271
Clinton
2 Light Flush
 Satin Nickel Finish
 with White Alabaster Glass
 Height: 5.63" Diameter: 13"
 Use (2) Medium (E26) Base Lamps,
 60 Watt Maximum



62236
Trinity II
1 Light Flush
 Oil Rubbed Bronze Finish
 with Aged Alabaster Glass
 Height: 5.88" Diameter: 11.25"
 Use (1) Medium (E26) Base Lamp,
 60 Watt Maximum

62237
Trinity II
2 Light Flush
 Oil Rubbed Bronze Finish
 with Aged Alabaster Glass
 Height: 6.63" Diameter: 13.13"
 Use (2) Medium (E26) Base Lamps,
 60 Watt Maximum

64308
2 Light Flush
 Sienna Finish
 with Frosted Swirl Glass
 Height: 6.13" Diameter: 13"
 Use (2) Medium (E26) Base Lamps,
 60 Watt Maximum



62225
Elena
1 Light Flush
 Dark Bronze Finish
 with Antique Amber Glass
 Height: 6.25" Diameter: 11"
 Use (1) Medium (E26) Base Lamp,
 60 Watt Maximum

66028
Elena
2 Light Flush
 Dark Bronze Finish
 with Antique Amber Glass
 Height: 6.75" Diameter: 13"
 Use (2) Medium (E26) Base Lamps,
 60 Watt Maximum

66253
Pine Creek
2 Light Flush
 Iron Granite Finish
 with Frosted Glass
 Height: 6.38" Diameter: 13.25"
 Use (2) Medium (E26) Base Lamps,
 60 Watt Maximum



62231
Chapel Hill
1 Light Flush
 Oil Rubbed Bronze Finish
 with Antique Bronze Scavo Glass
 Height: 6.13" Diameter: 11"
 Use (1) Medium (E26) Base Lamp,
 60 Watt Maximum

66599
Spring Valley
2 Light Flush
 Ebony Bronze Finish
 with Aged Alabaster Glass
 Height: 6" Diameter: 13"
 Use (2) Medium (E26) Base Lamps,
 60 Watt Maximum



62203
Wensley
1 Light Flush
*Oil Rubbed Bronze Finish
 with White Alabaster Glass*
 Height: 6" Diameter: 11.25"
 Use (1) Medium (E26) Base Lamp,
 60 Watt Maximum



66223
Wensley
2 Light Semi-Flush
*Oil Rubbed Bronze Finish
 with White Alabaster Glass*
 Height: 6.5" Diameter: 10.13"
 Use (2) Medium (E26) Base Lamps,
 60 Watt Maximum



62219
Kings Canyon
2 Light Flush
*Oil Rubbed Bronze Finish
 with Burnt Scavo Glass*
 Height: 7.25" Diameter: 13.25"
 Use (2) Medium (E26) Base Lamps,
 60 Watt Maximum



62244
Treebridge Station
2 Light Flush
*Espresso Finish
 with White Alabaster Glass*
 Height: 5.63" Diameter: 13.5"
 Use (2) Medium (E26) Base Lamps,
 60 Watt Maximum



64290
1 Light Flush
*Oil Rubbed Bronze Finish
 with Frosted White Alabaster Glass*
 Height: 5.5" Diameter: 11"
 Use (1) Medium (E26) Base Lamp,
 60 Watt Maximum



64291
2 Light Flush
*Oil Rubbed Bronze Finish
 with Frosted White Alabaster Glass*
 Height: 5.88" Diameter: 13"
 Use (2) Medium (E26) Base Lamps,
 60 Watt Maximum



64292
3 Light Flush
*Oil Rubbed Bronze Finish
 with Frosted White Alabaster Glass*
 Height: 6.63" Diameter: 15"
 Use (3) Medium (E26) Base Lamps,
 60 Watt Maximum



62211
Regal Springs
2 Light Flush
 Ebony Gold Finish
 with Burnt Scavo Glass
 Height: 7.5" Diameter: 13.75"
 Use (2) Medium (E26) Base Lamps,
 60 Watt Maximum



62210
Regal Springs
2 Light Semi-Flush
 Ebony Gold Finish
 with Burnt Scavo Glass
 Height: 12.5" Width: 13"
 Use (2) Medium (E26) Base Lamps,
 60 Watt Maximum



66254
Pine Creek
2 Light Semi-Flush
 Iron Granite Finish
 with Frosted Glass
 Height: 12.25" Width: 14.5"
 Use (2) Medium (E26) Base Lamps,
 60 Watt Maximum



69193
Provincial
2 Light Flush
 Excavated Bronze Finish
 with Frosted Rope and Reed Design Glass
 Height: 6" Diameter: 13"
 Use (2) Medium (E26) Base Lamps,
 60 Watt Maximum



69192
Provincial
2 Light Flush
 Excavated Bronze Finish
 with Frosted Rope and Reed Design Glass
 Height: 5.5" Diameter: 11"
 Use (2) Candelabra (E12) Base Lamps,
 40 Watt Maximum



67241
San Moritz
2 Light Flush
 Cozumel Gold Finish
 with Marbleized Alabaster Glass
 Height: 6.5" Diameter: 13.25"
 Use (2) Medium (E26) Base Lamps,
 60 Watt Maximum



66177
3 Light Flush
 Cozumel Gold Finish
 with Frosted Embossed Floral and
 Leaf Design Glass
 Height: 7.63" Diameter: 15"
 Use (3) Medium (E26) Base Lamps,
 60 Watt Maximum



64311
2 Light Flush
 Cozumel Gold Finish
 with Frosted Swirl Glass
 Height: 6.13" Diameter: 13"
 Use (2) Medium (E26) Base Lamps,
 60 Watt Maximum



64316
2 Light Flush
Sienna Finish
with Embossed Floral and Leaf Design Glass
Height: 7" Diameter: 13"
Use (2) Medium (E26) Base Lamps, 60 Watt Maximum



67225
Sierra Madre
2 Light Flush
Organic Gold Finish
with Frosted White Alabaster Glass
Height: 6.25" Diameter: 15.38"
Use (2) Medium (E26) Base Lamps, 75 Watt Maximum



64309
3 Light Flush
Sienna Finish
with Frosted Swirl Glass
Height: 6.5" Diameter: 15"
Use (3) Medium (E26) Base Lamps, 60 Watt Maximum



67142
2 Light Flush
Sienna Finish
with Frosted Ribbed Glass
Height: 7.5" Diameter: 13.25"
Use (2) Medium (E26) Base Lamps, 60 Watt Maximum



69246
Laurel Springs
2 Light Flush
Antique Brick Finish
with Frosted Crackle Glass
Height: 6.63" Diameter: 13"
Use (2) Medium (E26) Base Lamps, 60 Watt Maximum



69449
Conestoga
2 Light Flush
Saddle Bronze Finish
with Antique Amber Scavo Glass
Height: 7.13" Diameter: 15"
Use (2) Medium (E26) Base Lamps, 75 Watt Maximum



69450
Conestoga
2 Light Flush
Saddle Bronze Finish
with Antique Amber Scavo Glass
Height: 6.75" Diameter: 13"
Use (2) Medium (E26) Base Lamps, 60 Watt Maximum



64363
2 Light Flush
 Brushed Nickel Finish
 with Frosted Glass
 Height: 5.5" Diameter: 13"
 Use (2) GU24 Base CFL
 Twist Lamps, 13 Watt,
 Lamps Included



66645
Churchville
3 Light Flush
 Brushed Nickel Finish
 with Frosted White Alabaster Glass
 Height: 7.38" Diameter: 15"
 Use (3) Medium (E26) Base Lamps,
 60 Watt Maximum



66646
Churchville
2 Light Flush
 Brushed Nickel Finish
 with Frosted White Alabaster Glass
 Height: 6.13" Diameter: 13.25"
 Use (2) Medium (E26) Base Lamps,
 60 Watt Maximum



67572
Eastgate
1 Light Flush
 Brushed Nickel Finish
 with Frosted White Alabaster Glass
 Height: 5.25" Diameter: 10.25"
 Use (1) Medium (E26) Base Lamp,
 75 Watt Maximum



67573
Eastgate
2 Light Flush
 Brushed Nickel Finish
 with Frosted White Alabaster Glass
 Height: 5.5" Diameter: 13"
 Use (2) Medium (E26) Base Lamps,
 60 Watt Maximum




64304
1 Light Flush
 Brushed Nickel Finish
 with Frosted Swirl Glass
 Height: 5.88" Diameter: 11"
 Use (1) Medium (E26) Base Lamp,
 60 Watt Maximum



64305
2 Light Flush
 Brushed Nickel Finish
 with Frosted Swirl Glass
 Height: 6.13" Diameter: 13"
 Use (2) Medium (E26) Base Lamps,
 60 Watt Maximum



64306
3 Light Flush
 Brushed Nickel Finish
 with Frosted Swirl Glass
 Height: 6.5" Diameter: 15"
 Use (3) Medium (E26) Base Lamps,
 60 Watt Maximum

Compact Fluorescent Lamps contain mercury.  For more on clean up and safe disposal, visit epa.gov/cfl.



64301

3 Light Flush

*White Finish
with Frosted Swirl Glass*

Height: 6.5" Diameter: 15"

*Use (3) Medium (E26) Base Lamps,
60 Watt Maximum*



64300

2 Light Flush

*White Finish
with Frosted Swirl Glass*

Height: 6.13" Diameter: 13"

*Use (2) Medium (E26) Base Lamps,
60 Watt Maximum*



66378

1 Light Flush

*White Finish
with Frosted Swirl Glass*

Height: 5.88" Diameter: 11"

*Use (1) Medium (E26) Base Lamp,
60 Watt Maximum*



66176

3 Light Flush

*Textured White Finish
with Embossed Floral
and Leaf Design Glass*

Height: 7.25" Diameter: 15"

*Use (3) Medium (E26) Base Lamps,
60 Watt Maximum*



66162

2 Light Flush

*Textured White Finish
with Embossed Floral
and Leaf Design Glass*

Height: 7" Diameter: 13.25"

*Use (2) Medium (E26) Base Lamps,
60 Watt Maximum*



66161

1 Light Flush

*Textured White Finish
with Embossed Floral
and Leaf Design Glass*

Height: 6.25" Diameter: 11.25"

*Use (1) Medium (E26) Base Lamp,
60 Watt Maximum*



64303

3 Light Flush

*Polished Brass Finish
with Frosted Swirl Glass*

Height: 6.5" Diameter: 15"

*Use (3) Medium (E26) Base Lamps,
60 Watt Maximum*



64302

2 Light Flush

*Polished Brass Finish
with Frosted Swirl Glass*

Height: 6.13" Diameter: 13"

*Use (2) Medium (E26) Base Lamps,
60 Watt Maximum*



66327

1 Light Flush

*Polished Brass Finish
with Frosted Swirl Glass*

Height: 5.88" Diameter: 11"

*Use (1) Medium (E26) Base Lamp,
60 Watt Maximum*



66465

3 Light Flush

*Polished Brass Finish
with Crystal Ribbed Glass*

Height: 8.25" Diameter: 15.38"

*Use (3) Medium (E26) Base Lamps,
60 Watt Maximum*



66282

2 Light Flush

*Polished Brass Finish
with Crystal Ribbed Glass*

Height: 7.25" Diameter: 13.5"

*Use (2) Medium (E26) Base Lamps,
60 Watt Maximum*



66464

1 Light Flush

*Polished Brass Finish
with Crystal Ribbed Glass*

Height: 6.25" Diameter: 11"

*Use (1) Medium (E26) Base Lamp,
75 Watt Maximum*



66323

2 Light Semi-Flush

*Polished Brass Finish
with Clear Ribbed and
Etched Floral Pattern Glass*

Height: 8.25" Diameter: 11.75"

*Use (2) Medium (E26) Base Lamps,
60 Watt Maximum*



64361

2 Light Flush

*Cobblestone Finish
with Frosted Ribbed Glass*

Height: 7.25" Diameter: 13"

*Use (2) Medium (E26) Base Lamps,
60 Watt Maximum*



67605

1 Light Flush

*Cobblestone Finish
with Frosted White Alabaster Glass*

Height: 6.75" Diameter: 11"

*Use (1) Medium (E26) Base Lamp,
60 Watt Maximum*



64323

2 Light Flush

*Pewter Patina Finish
with Frosted Ribbed Glass*

Height: 7.25" Diameter: 12.5"

*Use (2) Medium (E26) Base Lamps,
60 Watt Maximum*



66339

2 Light Flush

*Bisque Leaf Finish
with Faux Marbleized Glass Bowl
Height: 5" Diameter: 11.75"
Use (2) Candelabra (E12) Base Lamps,
40 Watt Maximum*



64358

3 Light Flush

*White Finish
with Frosted White Alabaster Glass
Height: 6.75" Diameter: 15"
Use (3) Medium (E26) Base Lamps,
60 Watt Maximum*



64360

3 Light Flush

*Brushed Nickel Finish with
Frosted White Alabaster Glass
Height: 6.75" Diameter: 15"
Use (3) Medium (E26) Base Lamps,
60 Watt Maximum*



67314

2 Light Flush

*Antique Brass Finish
with White Glass
Height: 6.75" Diameter: 9.5"
Use (2) Medium (E26) Base Lamps,
60 Watt Maximum*



64321

2 Light Flush

*Brushed Nickel Finish
with Etched Glass
Height: 6.75" Diameter: 9.5"
Use (2) Medium (E26) Base Lamps,
60 Watt Maximum*



64340

2 Light Semi-Flush

*Brushed Nickel Finish
with Frosted Glass
Height: 8" Diameter: 15.25"
Use (2) Medium (E26) Base Lamps,
60 Watt Maximum*



66468

2 Light Semi-Flush

*Polished Brass Finish
with White and Clear Glass
Height: 7.5" Diameter: 15.25"
Use (2) Medium (E26) Base Lamps,
60 Watt Maximum*



66689
1 Light Flush
 Polished Brass Finish
 with Clear Faceted Glass
 Height: 4.75" Diameter: 7.5"
 Use (1) Medium (E26) Base Lamp,
 60 Watt Maximum



66698
2 Light Flush
 Polished Brass Finish
 with Clear Faceted Glass
 Height: 5.5" Diameter: 9.5"
 Use (2) Medium (E26) Base Lamps,
 60 Watt Maximum



66610
2 Light Flush
 Antique Brass Finish
 with Clear Faceted Glass
 Height: 5.5" Diameter: 9.5"
 Use (2) Medium (E26) Base Lamps,
 60 Watt Maximum



67209
1 Light Flush
 Brushed Nickel Finish
 with Frosted Fluted Glass
 Height: 4" Diameter: 6.88"
 Use (1) Medium (E26) Base Lamp,
 60 Watt Maximum



67210
2 Light Flush with Pull Chain
 Brushed Nickel Finish
 with Frosted Fluted Glass
 Height: 4.25" Diameter: 8.75"
 Use (2) Medium (E26) Base Lamps,
 60 Watt Maximum



67212
2 Light Flush
 Brushed Nickel Finish
 with Frosted Fluted Glass
 Height: 5.75" Diameter: 10.75"
 Use (2) Medium (E26) Base Lamps,
 60 Watt Maximum



66329
1 Light Flush
 Polished Brass Finish
 with Satin White Ribbed Glass
 Height: 4.63" Diameter: 8"
 Use (1) Medium (E26) Base Lamp,
 60 Watt Maximum



67202
2 Light Flush with Pull Chain
 Sienna Finish
 with Frosted Fluted Glass
 Height: 4.25" Diameter: 8.75"
 Use (2) Medium (E26) Base Lamps,
 60 Watt Maximum



66609
2 Light Flush
 Polished Brass Finish
 with White Glass
 Height: 4.75" Diameter: 8.88"
 Use (2) Medium (E26) Base Lamps,
 60 Watt Maximum



66611
2 Light Flush
 White Finish
 with White Glass
 Height: 5" Diameter: 8.75"
 Use (2) Medium (E26) Base Lamps,
 60 Watt Maximum



66699
1 Light Flush
 White Finish
 with White Glass
 Height: 4.38" Diameter: 7.25"
 Use (1) Medium (E26) Base Lamp,
 60 Watt Maximum



66681
1 Light Flush
 Antique Brass Finish
 with White Glass
 Height: 4.38" Diameter: 7.25"
 Use (1) Medium (E26) Base Lamp,
 60 Watt Maximum



66678
1 Light Flush
 Polished Brass Finish
 with Satin White Glass with Design
 Height: 4.5" Diameter: 7.5"
 Use (1) Medium (E26) Base Lamp,
 60 Watt Maximum



66604
1 Light Flush
 Antique Brass Finish
 with Satin White Glass with Design
 Height: 4.5" Diameter: 7.5"
 Use (1) Medium (E26) Base Lamp,
 60 Watt Maximum



67215
2 Light Flush with Pull Chain
 Polished Brass Finish
 with Frosted Fluted Glass
 Height: 4.25" Diameter: 8.75"
 Use (2) Medium (E26) Base Lamps,
 60 Watt Maximum



66658
1 Light Flush
 Polished Brass Finish
 with Clear Acorn Design Glass
 Height: 7.25" Diameter: 5.25"
 Use (1) Medium (E26) Base Lamp,
 60 Watt Maximum



66600
1 Light Flush
 Antique Brass Finish
 with White Glass Globe
 Height: 7.25" Diameter: 6"
 Use (1) Medium (E26) Base Lamp,
 60 Watt Maximum



66692
1 Light Flush
 Polished Brass Finish
 with Crystal Ribbed Glass Globe
 Height: 7.25" Diameter: 6"
 Use (1) Medium (E26) Base Lamp,
 60 Watt Maximum



66677
1 Light Flush
 Polished Brass Finish
 with White Glass Globe
 Height: 7.25" Diameter: 6"
 Use (1) Medium (E26) Base Lamp,
 60 Watt Maximum



66607
1 Light Flush
 White Finish
 with White Glass Globe
 Height: 7.25" Diameter: 6"
 Use (1) Medium (E26) Base Lamp,
 60 Watt Maximum



66680
1 Light Flush with Pull Chain
 White Finish
 with White Glass Globe
 Height: 7.25" Diameter: 6"
 Use (1) Medium (E26) Base Lamp,
 60 Watt Maximum



67208
1 Light Flush with Pull Chain
 Brushed Nickel Finish
 with White Glass Globe
 Height: 7.25" Diameter: 6"
 Use (1) Medium (E26) Base Lamp,
 60 Watt Maximum



66603
1 Light Flush
 Polished Brass Finish
 with Frosted and Clear Glass
 Height: 7.25" Diameter: 6"
 Use (1) Medium (E26) Base Lamp,
 60 Watt Maximum



66214

3 Light Flush

White Finish
with White Glass Globes
Height: 7.25" Diameter: 16"
Use (3) Medium (E26) Base Lamps,
60 Watt Maximum



67345

2 Light Flush with Pull Chain

White Finish
with White and Clear Glass
Height: 5.25" Diameter: 8.75"
Use (2) Medium (E26) Base Lamps,
60 Watt Maximum



66204

1 Light Flush

White Finish
with White and Clear Glass
Height: 4.5" Diameter: 6.75"
Use (1) Medium (E26) Base Lamp,
60 Watt Maximum



66203

2 Light Flush

White Finish
with White and Clear Glass
Height: 5.25" Diameter: 8.75"
Use (2) Medium (E26) Base Lamps,
60 Watt Maximum



66238

2 Light Flush

White Finish
with White and Clear Glass
Height: 5.25" Diameter: 10.75"
Use (2) Medium (E26) Base Lamps,
75 Watt Maximum



66239

1 Light Flush

Chrome Finish
with White and Clear Glass
Height: 4.5" Diameter: 6.75"
Use (1) Medium (E26) Base Lamp,
60 Watt Maximum



66240

2 Light Flush

Chrome Finish
with White and Clear Glass
Height: 5.25" Diameter: 8.75"
Use (2) Medium (E26) Base Lamps,
60 Watt Maximum



66241

2 Light Flush

Chrome Finish
with White and Clear Glass
Height: 5.25" Diameter: 10.75"
Use (2) Medium (E26) Base Lamps,
75 Watt Maximum



66205
3 Light Semi-Flush
 Polished Brass Finish
 with White Glass
 Height: 7" Diameter: 15"
 Use (3) Medium (E26) Base Lamps,
 60 Watt Maximum



66206
2 Light Semi-Flush
 White Finish
 with White Scroll Design Glass
 Height: 6.25" Diameter: 13"
 Use (2) Medium (E26) Base Lamps,
 60 Watt Maximum



66263
2 Light Semi-Flush
 White Finish
 with White and Clear Glass
 Height: 6.25" Square: 11.5"
 Use (2) Medium (E26) Base Lamps,
 60 Watt Maximum



66242
2 Light Semi-Flush
 White Finish
 with White Glass
 Height: 6.5" Diameter: 13"
 Use (2) Medium (E26) Base Lamps,
 60 Watt Maximum



66201
2 Light Semi-Flush
 White Finish
 with White Glass
 Height: 6" Square: 12"
 Use (2) Medium (E26) Base Lamps,
 60 Watt Maximum



66297
1 Light Flush Mount
 White and Brushed Nickel Finish
 with White Alabaster Glass
 Height: 4.25" Diameter: 12"
 Use (1) Medium (E26) Base Lamp,
 60 Watt Maximum



66200
**2 Light Semi-Flush
 with Pull Chain**
 White Finish
 with White Glass
 Height: 6.63" Square: 12"
 Use (2) Medium (E26) Base Lamps,
 60 Watt Maximum



65302
1 Light Flush
 Brushed Nickel Finish
 with Amber Diffuser and Multi-color Designs
 Height: 3.88" Diameter: 9.75"
 Use (1) Candelabra (E12) Base Lamp,
 60 Watt Maximum



67322

3 Light Flush

*Brushed Nickel Finish
with Opal Glass*

Height: 5.5" Width: 18"

*Use (3) Medium (E26) Base Lamps,
60 Watt Maximum*



67325

3 Light Flush

*Polished Brass Finish
with Clear Floral Ribbed Glass Shade*

Height: 5.5" Width: 18"

*Use (3) Medium (E26) Base Lamps,
60 Watt Maximum*



66686

3 Light Flush

*Antique Brass Finish
with Frosted Ruffled Edge Glass*

Height: 6" Width: 11"

*Use (3) Medium (E26) Base Lamps,
60 Watt Maximum*



66326

**3 Light Multi-
Directional Flush**

White Finish

Height: 8.25" Width: 10.19"

Extends: 18.25"

*Use (3) Medium (E26) Base Lamps,
65 Watt Maximum*



66624

**1 Light Multi-
Directional Flush**

White Finish

Height: 8.25" Width: 5.5"

Extends: 9"

*Use (1) Medium (E26) Base Lamp,
60 Watt Maximum*



WALL

interior light fixture assortment

Utilize the versatility of wall fixtures to enhance the beauty of a fireplace, accentuate nooks and quiet spaces, or add a decorative touch around a bathroom mirror. The possibilities are endless.





*** 66596**
Spring Valley
3 Light Wall
 Ebony Bronze Finish
 with Aged Alabaster Glass
 Height: 9.5" Width: 25"
 Extends: 8.25"
 Use (3) Medium (E26) Base Lamps,
 100 Watt Maximum



*** 62212**
Regal Springs
1 Light Wall
 Ebony Gold Finish
 with Burnt Scavo Glass
 Height: 9.5" Width: 7"
 Extends: 9"
 Use (1) Medium (E26) Base Lamp,
 60 Watt Maximum



*** 62213**
Regal Springs
3 Light Wall
 Ebony Gold Finish
 with Burnt Scavo Glass
 Height: 9.5" Width: 25.25"
 Extends: 9"
 Use (3) Medium (E26) Base Lamps,
 60 Watt Maximum



*** 62204**
Wensley
1 Light Wall
 Oil Rubbed Bronze Finish
 with White Alabaster Glass
 Height: 7.13" Width: 5.88"
 Extends: 8.13"
 Use (1) Medium (E26) Base Lamp,
 60 Watt Maximum



*** 62205**
Wensley
2 Light Wall
 Oil Rubbed Bronze Finish
 with White Alabaster Glass
 Height: 7.13" Width: 14.25"
 Extends: 8.13"
 Use (2) Medium (E26) Base Lamps,
 60 Watt Maximum



*** 66220**
Wensley
3 Light Wall
 Oil Rubbed Bronze Finish
 with White Alabaster Glass
 Height: 7.13" Width: 23.38"
 Extends: 8.13"
 Use (3) Medium (E26) Base Lamps,
 60 Watt Maximum



*** 62245**
Treebridge Station
1 Light Wall
 Espresso Finish
 with White Alabaster Glass
 Height: 10.5" Width: 5"
 Extends: 7.5"
 Use (1) Medium (E26) Base Lamp,
 60 Watt Maximum



*** 62247**
Treebridge Station
3 Light Wall
 Espresso Finish
 with White Alabaster Glass
 Height: 10.5" Width: 21.25"
 Extends: 7.5"
 Use (3) Medium (E26) Base Lamps,
 60 Watt Maximum

*Fixture can be installed up or down
www.westinghouselighting.com



***62238**
Trinity II
1 Light Wall
 Oil Rubbed Bronze Finish
 with Aged Alabaster Glass
 Height: 9" Width: 5.13"
 Extends: 8"
 Use (1) Medium (E26) Base Lamp,
 60 Watt Maximum



***62239**
Trinity II
3 Light Wall
 Oil Rubbed Bronze Finish
 with Aged Alabaster Glass
 Height: 8.5" Width: 17.25"
 Extends: 8.38"
 Use (3) Medium (E26) Base Lamps,
 60 Watt Maximum



***69009**
Hearthstone
3 Light Wall
 Burnished Bronze Patina Finish
 with Burnt Scavo Glass
 Height: 10.75" Width: 19.5"
 Extends: 8"
 Use (3) Medium (E26) Base Lamps,
 60 Watt Maximum



***62227**
Elena
1 Light Wall
 Dark Bronze Finish
 with Antique Amber Glass
 Height: 8.63" Width: 6.25"
 Extends: 9"
 Use (1) Medium (E26) Base Lamp,
 60 Watt Maximum



***66031**
Elena
3 Light Wall
 Dark Bronze Finish
 with Antique Amber Glass
 Height: 8.88" Width: 24"
 Extends: 10.5"
 Use (3) Medium (E26) Base Lamps,
 60 Watt Maximum



***62233**
Chapel Hill
1 Light Wall
 Oil Rubbed Bronze Finish
 with Antique Amber Scavo Glass
 Height: 9.13" Width: 5.13"
 Extends: 8.63"
 Use (1) Medium (E26) Base Lamp,
 60 Watt Maximum



***62234**
Chapel Hill
3 Light Wall
 Oil Rubbed Bronze Finish
 with Antique Amber Scavo Glass
 Height: 9.13" Width: 18.88"
 Extends: 8.63"
 Use (3) Medium (E26) Base Lamps,
 60 Watt Maximum

*Fixture can be installed up or down



*** 62220**
Kings Canyon
1 Light Wall
 Oil Rubbed Bronze Finish
 with Burnt Scavo Glass
 Height: 9.13" Width: 7"
 Extends: 9"
 Use (1) Medium (E26) Base Lamp,
 60 Watt Maximum



*** 62221**
Kings Canyon
2 Light Wall
 Oil Rubbed Bronze Finish
 with Burnt Scavo Glass
 Height: 9.13" Width: 17"
 Extends: 9"
 Use (2) Medium (E26) Base Lamps,
 60 Watt Maximum



*** 62222**
Kings Canyon
3 Light Wall
 Oil Rubbed Bronze Finish
 with Burnt Scavo Glass
 Height: 9.13" Width: 25"
 Extends: 9"
 Use (3) Medium (E26) Base Lamps,
 60 Watt Maximum



*** 67015**
Abington
1 Light Wall
 Weathered Bronze Finish
 with Frosted Glass
 Height: 8.25" Width: 7.25"
 Extends: 8"
 Use (1) Candelabra (E12) Base Lamp,
 60 Watt Maximum



*** 66592**
Spring Valley
1 Light Wall
 Ebony Bronze Finish
 with Aged Alabaster Glass
 Height: 9.25" Width: 7"
 Extends: 8"
 Use (1) Medium (E26) Base Lamp,
 100 Watt Maximum



*** 66593**
Spring Valley
2 Light Wall
 Ebony Bronze Finish
 with Aged Alabaster Glass
 Height: 9.5" Width: 16"
 Extends: 8"
 Use (2) Medium (E26) Base Lamps,
 100 Watt Maximum



*** 62260**
Parker Mews
1 Light Wall
 Brushed Nickel Finish
 with White Linen Fabric Shade
 Height: 9.75" Width: 5.5"
 Extends: 7"
 Use (1) Candelabra (E12) Base Lamp,
 60 Watt Maximum



*** 62261**
Parker Mews
2 Light Wall
 Brushed Nickel Finish
 with White Linen Fabric Shades
 Height: 9.75" Width: 16"
 Extends: 7"
 Use (2) Candelabra (E12) Base Lamps,
 60 Watt Maximum



*** 62262**
Parker Mews
3 Light Wall
 Brushed Nickel Finish
 with White Linen Fabric Shades
 Height: 9.75" Width: 24"
 Extends: 7"
 Use (3) Candelabra (E12) Base Lamps,
 60 Watt Maximum

*Fixture can be installed up or down
www.westinghouselighting.com



*** 62278**
Sylvestre
1 Light Wall
 Brushed Nickel Finish
 with Frosted Seeded Glass
 Height: 8.25" Width: 4.75"
 Extends: 6.25"
 Use (1) Medium (E26) Base Lamp,
 60 Watt Maximum



*** 62279**
Sylvestre
3 Light Wall
 Brushed Nickel Finish
 with Frosted Seeded Glass
 Height: 8.25" Width: 15.75"
 Extends: 6.25"
 Use (3) Medium (E26) Base Lamps,
 60 Watt Maximum



*** 67331**
1 Light Wall
 Brushed Nickel Finish
 with Frosted White Alabaster Glass
 Height: 8.5" Width: 7.5"
 Extends: 8.75"
 Use (1) Medium (E26) Base Lamp,
 100 Watt Maximum



*** 67899**
Royal Park
3 Light Wall
 Brushed Nickel Finish
 with Frosted White Opal Glass
 Height: 9.25" Width: 25.88"
 Extends: 8.37"
 Use (3) Medium (E26) Base Lamps,
 100 Watt Maximum



*** 62311**
Elena II
2 Light Wall
 Chrome Finish
 with Honey Swirl Scavo Glass
 Height: 9" Width: 15.87"
 Extends: 11"
 Use (2) Medium (E26) Base Lamps,
 60 Watt Maximum




*** 62312**
Elena II
3 Light Wall
 Chrome Finish
 with Honey Swirl Scavo Glass
 Height: 9" Width: 24.75"
 Extends: 11"
 Use (3) Medium (E26) Base Lamps,
 60 Watt Maximum

*Fixture can be installed up or down



*** 62272**
Clinton
1 Light Wall
 Satin Nickel Finish
 with White Alabaster Glass
 Height: 9.25" Width: 5.88"
 Extends: 8.38"
 Use (1) Medium (E26) Base Lamp,
 60 Watt Maximum



*** 62273**
Clinton
3 Light Wall
 Satin Nickel Finish
 with White Alabaster Glass
 Height: 9.25" Width: 22"
 Extends: 8.38"
 Use (3) Medium (E26) Base Lamps,
 60 Watt Maximum



*** 62284**
Swanstone
1 Light Wall
 Satin Nickel Finish
 with White Opal Glass
 Height: 7.5" Width: 7.13"
 Extends: 9.63"
 Use (1) Medium (E26) Base Lamp,
 60 Watt Maximum



*** 62285**
Swanstone
3 Light Wall
 Satin Nickel Finish
 with White Opal Glass
 Height: 8.25" Width: 24.25"
 Extends: 9.38"
 Use (3) Medium (E26) Base Lamps,
 60 Watt Maximum



*** 66647**
Churchville
1 Light Wall
 Brushed Nickel Finish
 with Frosted White Alabaster Glass
 Height: 8" Width: 7"
 Extends: 8" Use (1) Medium (E26)
 Base Lamp, 100 Watt Maximum



*** 66649**
Churchville
3 Light Wall
 Brushed Nickel Finish
 with Frosted White Alabaster Glass
 Height: 7.5" Width: 25"
 Extends: 8.5"
 Use (3) Medium (E26) Base Lamps,
 100 Watt Maximum



*** 62267**
Fontane
1 Light Wall
 Brushed Nickel Finish
 with Frosted Glass
 Height: 8.63" Width: 6.5"
 Extends: 7.88"
 Use (1) Medium (E26) Base Lamp,
 60 Watt Maximum



*** 62288**
Fallon
3 Light Wall
 Satin Platinum Finish
 with White Alabaster Glass
 Height: 7.25" Width: 27.75"
 Extends: 10.5"
 Use (3) Medium (E26) Base Lamps,
 60 Watt Maximum

*Fixture can be installed up or down
www.westinghouselighting.com

*** 67514**
1 Light Wall with On/Off Switch

Oyster Bronze Finish
 with Frosted Ribbed Design Glass
 Height: 8" Width: 4.75"
 Extends: 9.5"
 Use (1) Medium (E26) Base Lamp,
 100 Watt Maximum



*** 67515**
3 Light Wall

Oyster Bronze Finish
 with Frosted Ribbed Design Glass
 Height: 8.75" Width: 16.5"
 Extends: 9.5"
 Use (3) Medium (E26) Base Lamps,
 100 Watt Maximum



*** 67512**
1 Light Wall with On/Off Switch

Oyster Bronze Finish
 with Frosted Ribbed Glass
 Height: 9.25" Width: 5"
 Extends: 8.25"
 Use (1) Medium (E26) Base Lamp,
 100 Watt Maximum



*** 67513**
3 Light Wall

Oyster Bronze Finish
 with Frosted Ribbed Glass
 Height: 8.5" Width: 24"
 Extends: 8.25"
 Use (3) Medium (E26) Base Lamps,
 100 Watt Maximum



*** 66522**
3 Light Wall

Chrome Finish
 with Frosted Pleated Glass
 Height: 8.5" Width: 24"
 Extends: 7.25"
 Use (3) Medium (E26) Base Lamps,
 100 Watt Maximum

*** 66523**
4 Light Wall

Chrome Finish
 with Frosted Pleated Glass
 Height: 8.5" Width: 30"
 Extends: 7.25"
 Use (4) Medium (E26) Base Lamps,
 100 Watt Maximum

*** 66521**
1 Light Wall with On/Off Switch

Chrome Finish
 with Frosted Pleated Glass
 Height: 9.38" Width: 5"
 Extends: 7.62"
 Use (1) Medium (E26) Base Lamp,
 100 Watt Maximum



*** 67477**
3 Light Wall

Chrome Finish
 with Frosted Tulip Glass
 Height: 8.25" Width: 24"
 Extends: 6.75"
 Use (3) Medium (E26) Base Lamps,
 100 Watt Maximum



*Fixture can be installed up or down



*** 66494**
1 Light Wall with On/Off Switch
Antique Pewter Finish with Frosted Pleated Glass
 Height: 9.75" Width: 5"
 Extends: 7.75"
 Use (1) Medium (E26) Base Lamp, 100 Watt Maximum



*** 66490**
1 Light Wall with On/Off Switch
Cobblestone Finish with Frosted White Alabaster Glass
 Height: 9.13" Width: 5.5"
 Extends: 8.75"
 Use (1) Medium (E26) Base Lamp, 100 Watt Maximum



*** 66492**
1 Light Wall with On/Off Switch
Goldenrod Finish with Frosted Glass
 Height: 9.75" Width: 5"
 Extends: 7.75"
 Use (1) Medium (E26) Base Lamp, 100 Watt Maximum



*** 66495**
3 Light Wall
Antique Pewter Finish with Frosted Pleated Glass
 Height: 7.75" Width: 18" Extends: 7.75"
 Use (3) Medium (E26) Base Lamps, 100 Watt Maximum



*** 66491**
3 Light Wall
Cobblestone Finish with Frosted White Alabaster Glass
 Height: 8.75" Width: 24" Extends: 8.5"
 Use (3) Medium (E26) Base Lamps, 100 Watt Maximum



*** 67533**
3 Light Wall
White Finish with Embossed Floral and Leaf Design Glass
 Height: 8.75" Width: 18" Extends: 8.37"
 Use (3) Medium (E26) Base Lamps, 100 Watt Maximum



*** 66499**
3 Light Wall
Cobblestone Finish with Frosted Glass
 Height: 8.25" Width: 17" Extends: 7.87"
 Use (3) Medium (E26) Base Lamps, 100 Watt Maximum

*Fixture can be installed up or down
www.westinghouselighting.com



*** 67226**
Sierra Madre
1 Light Wall
Organic Gold Finish
with Frosted White Alabaster Glass
Height: 9.38" Width: 7" Extends: 8.25"
Use (1) Candelabra (E12) Base Lamp,
60 Watt Maximum



69234
Laurel Springs
1 Light Wall with
On/Off Switch
Antique Brick Finish
with Frosted Crackle Glass
Height: 10.5" Width: 5" Extends: 7.75"
Use (1) Candelabra (E12) Base Lamp,
60 Watt Maximum



*** 66496**
1 Light Wall
Brushed Nickel Finish
with White Opal Glass
Height: 9" Width: 5.13"
Extends: 8"
Use (1) Medium (E26) Base Lamp,
60 Watt Maximum



*** 64617**
2 Light Wall
Brushed Nickel Finish
with White Opal Glass
Height: 8.5" Width: 13.5"
Extends: 8.5"
Use (2) Medium (E26) Base Lamps,
60 Watt Maximum



*** 66497**
3 Light Wall
Brushed Nickel Finish
with White Opal Glass
Height: 8.5" Width: 17.25"
Extends: 8.37"
Use (3) Medium (E26) Base Lamps,
60 Watt Maximum



66662
1 Light Wall Sconce
Polished Brass Finish
with Crystal Ribbed Glass
Height: 6.5" Width: 12" Extends: 6"
Use (1) Medium (E26) Base Lamp,
100 Watt Maximum

*Fixture can be installed up or down

66601

1 Light Wall with On/Off Switch

Polished Brass Finish with Frosted Etched Grape Design Glass
 Height: 7.75" Width: 4.5"
 Extends: 4.87"

Use (1) Medium (E26) Base Lamp, 100 Watt Maximum



66654

1 Light Wall with On/Off Switch

Brushed Nickel Finish with White Opal Glass
 Height: 8" Width: 4.5"
 Extends: 5"

Use (1) Medium (E26) Base Lamp, 100 Watt Maximum



*** 66401**

1 Light Wall

White Finish Base with White Ceramic Glass
 Height: 7.5" Width: 4.5"
 Extends: 4.5"

Use (1) Medium (E26) Base Lamp, 75 Watt Maximum



66403

2 Light Wall with Ground Convenience Outlet

White Finish Base with White Ceramic Glass
 Height: 4.5" Width: 14" Extends: 5"
 Use (2) Medium (E26) Base Lamps, 75 Watt Maximum



66424

4 Light Wall with Ground Convenience Outlet

White Finish Base with White Ceramic Glass
 Height: 4.25" Width: 24" Extends: 5"
 Use (4) Medium (E26) Base Lamps, 60 Watt Maximum



66402

1 Light Wall with Ground Convenience Outlet and Pull Chain

Chrome Finish Base with White and Crystal Glass
 Height: 4.5" Width: 5.25"
 Extends: 6.5"

Use (1) Medium (E26) Base Lamp, 60 Watt Maximum

66405

3 Light Bath Bar

Polished Brass Finish
 Height: 4.25" Width: 18"
 Extends without Lamps: 2.12" Extends with Lamps: 5.25"
 Use (3) Medium (E26) Base Lamps, 100 Watt Maximum



66410

4 Light Bath Bar

Polished Brass Finish
 Height: 4.25" Width: 24"
 Extends without Lamps: 2.12" Extends with Lamps: 5.25"
 Use (4) Medium (E26) Base Lamps, 100 Watt Maximum



*Fixture can be installed up or down
www.westinghouselighting.com



66594
3 Light Bath Bar
 White Finish
 Height: 4.5" Width: 18"
 Extends without Lamps: 2.12" Extends with Lamps: 5.25"
 Use (3) Medium (E26) Base Lamps, 100 Watt Maximum



66595
4 Light Bath Bar
 White Finish
 Height: 4.5" Width: 24"
 Extends without Lamps: 2.12" Extends with Lamps: 5.25"
 Use (4) Medium (E26) Base Lamps, 100 Watt Maximum



66406
3 Light Bath Bar
 Chrome Finish
 Height: 4.5" Width: 18"
 Extends without Lamps: 2.12" Extends with Lamps: 5.25"
 Use (3) Medium (E26) Base Lamps, 100 Watt Maximum



66411
4 Light Bath Bar
 Chrome Finish
 Height: 4.5" Width: 24"
 Extends without Lamps: 2.12" Extends with Lamps: 5.25"
 Use (4) Medium (E26) Base Lamps, 100 Watt Maximum



66414
6 Light Bath Bar
 Chrome Finish
 Height: 4.5" Width: 36"
 Extends without Lamps: 2.25" Extends with Lamps: 5.25"
 Use (6) Medium (E26) Base Lamps, 100 Watt Maximum



66448
3 Light Bath Bar
 Beveled Mirror
 Height: 4.25" Width: 18"
 Extends without Lamps: 3.25" Extends with Lamps: 6.25"
 Use (3) Medium (E26) Base Lamps, 100 Watt Maximum



66449
4 Light Bath Bar
 Beveled Mirror
 Height: 4.25" Width: 24"
 Extends without Lamps: 3.25" Extends with Lamps: 6.25"
 Use (4) Medium (E26) Base Lamps, 100 Watt Maximum



66450
6 Light Bath Bar
 Beveled Mirror
 Height: 4.25" Width: 36"
 Extends without Lamps: 3.25" Extends with Lamps: 5.25"
 Use (6) Medium (E26) Base Lamps, 100 Watt Maximum



66442
3 Light Bath Bar
 Solid Oak with Polished Brass Finish
 Accented Socket Covers
 Height: 4.5" Width: 18"
 Extends without Lamps: 2.12" Extends with Lamps: 5.12"
 Use (3) Medium (E26) Base Lamps, 100 Watt Maximum



66443
4 Light Bath Bar
 Solid Oak with Polished Brass Finish
 Accented Socket Covers
 Height: 4.5" Width: 24"
 Extends without Lamps: 2.12" Extends with Lamps: 5.12"
 Use (4) Medium (E26) Base Lamps, 100 Watt Maximum

EXTERIOR

light fixture assortment

Welcome visitors and make a statement with the inviting glow of light and timeless, durable design of outdoor lighting fixtures.





new!

64000
9 Watt LED Wall Lantern
*Weathered Patina Finish
 with Seeded Glass*
 Height: 12.25" Width: 6" Extends: 8"
 Height from Center of Outlet Box: 2.83"
 Back Plate: H: 5.38" W: 4.38"
 Includes Integrated LEDs, 9 Watt Total



new!

64001
9 Watt LED Wall Lantern
*Black Finish
 with Clear Seeded Glass*
 Height: 11" Width: 6"
 Extends: 8"
 Height from Center of Outlet Box: 2.83"
 Back Plate: H: 5.38" W: 4.38"
 Includes Integrated LEDs, 9 Watt Total



new!

64002
9 Watt LED Wall Lantern
*Oil Rubbed Bronze Finish
 with Frosted Glass*
 Height: 14.63" Width: 6.25"
 Extends: 8.75"
 Height from Center of Outlet Box: 9.06"
 Back Plate: H: 7.88" W: 4.5"
 Includes Integrated LEDs, 9 Watt Total



new!

64003
9 Watt LED Wall Lantern
*Oil Rubbed Bronze Finish
 with Crackle Glass*
 Height: 9.75" Width: 6"
 Extends: 7.88"
 Height from Center of Outlet Box: 2.83"
 Back Plate: H: 5.38" W: 4.38"
 Includes Integrated LEDs, 9 Watt Total



new!

64004
9 Watt LED Wall Lantern
*Oil Rubbed Bronze Finish
 with Crackle Glass*
 Height: 14.63" Width: 9"
 Extends: 11.75"
 Height from Center of Outlet Box: 2.83"
 Back Plate: H: 8.88" W: 6.5"
 Includes Integrated LEDs, 9 Watt Total



LED LIGHT SOURCE SPECIFICATIONS

Item No.	Total Energy Used (Watts)	LED Chips Per Fixture	Watts Per LED Chip	Light Appearance (Kelvin)	Brightness (Lumens)	Avg. Rated Hours	Life in Years*	Est. Yearly Energy Cost**
64000	9	18	.5	3000 (Warm White)	500	40000	37	\$1.08
64001	9	18	.5	3000 (Warm White)	500	40000	37	\$1.08
64002	9	18	.5	3000 (Warm White)	500	40000	37	\$1.08
64003	9	18	.5	3000 (Warm White)	500	40000	37	\$1.08
64004	9	3	3	3000 (Warm White)	300	40000	37	\$1.08

*Based on 3hrs./day

**Based on 3hrs./day 11¢/kWh - Cost depends on rates and use.

**67543****Castle Inn****1 Light Wall Lantern**

Textured Black Finish
on Cast Aluminum with
Amber Seeded Glass

Height: 16.5" Width: 7.5" Extends: 9.25"

Height from Center
of Outlet Box: 6.37"

Back Plate: H: 9.5" W: 4.88"

Use (1) Medium (E26) Base Lamp,
100 Watt Maximum

**67545****Castle Inn****1 Light Pendant**

Textured Black Finish
on Cast Aluminum with
Amber Seeded Glass

Height: 14.63" Diameter: 7.5"

Chain: 36" Wire: 120"

Use (1) Medium (E26) Base Lamp,
100 Watt Maximum

62301**Weatherby****1 Light Wall Lantern**

Weathered Bronze Finish
on Steel with Clear Glass

Height: 12.75" Width: 6"

Extends: 7.5"

Height from Center
of Outlet Box: 7.25"

Back Plate: H: 7.88" W: 4.38"

Use (1) Medium (E26) Base Lamp,
60 Watt Maximum

**64841****Studenburg****1 Light Wall Lantern**

Vintage Bronze Finish
on Steel with Clear Crackle Glass

Height: 12.88" Width: 7"

Extends: 8.87"

Height from Center
of Outlet Box: 7.25"

Back Plate: H: 6.5" W: 4.13"

Use (1) Medium (E26) Base Lamp,
100 Watt Maximum

**64864****Riverbend****1 Light Wall Lantern**

Textured Rust Patina Finish
on Solid Brass and Steel with
Water Glass and Tiffany Accents

Height: 11" Width: 7" Extends: 7.75"

Height from Center
of Outlet Box: 3.63"

Back Plate: H: 6.75" W: 4.75"

Use (1) Medium (E26) Base Lamp,
100 Watt Maximum

**64865****Riverbend****1 Light Wall Lantern**

Textured Rust Patina Finish
on Solid Brass and Steel
with Water Glass and Tiffany Accents

Height: 14" Width: 9" Extends: 9.75"

Height from Center
of Outlet Box: 5"

Back Plate: H: 8.38" W: 4.75"

Use (1) Medium (E26) Base Lamp,
100 Watt Maximum

**64866****Riverbend****1 Light Post Top Lantern**

Textured Rust Patina Finish
on Solid Brass and Steel
with Water Glass and
Tiffany Accents

Height: 16.75" Width: 9"

Use (1) Medium (E26) Base Lamp,
100 Watt Maximum

(Fits standard 3" diameter post,
post sold separately)



62307

Parkville

1 Light Wall Lantern

Oil Rubbed Bronze Finish on Steel with White Alabaster Glass
 Height: 11" Width: 6.25" Extends: 8.37"
 Height from Center of Outlet Box: 2.25"
 Back Plate: D: 4.75"
 Use (1) Medium (E26) Base Lamp, 100 Watt Maximum



62302

Bonneville

1 Light Wall Lantern

Weathered Bronze Finish on Steel with Frosted Glass
 Height: 11.75" Width: 7.25" Extends: 8.88"
 Height from Center of Outlet Box: 4.75"
 Back Plate: D: 4.25"
 Use (1) Medium (E26) Base Lamp, 100 Watt Maximum



62303

Bonneville

2 Light Flush

Weathered Bronze Finish on Steel with Frosted Glass
 Height: 5.63" Diameter: 12.63"
 Use (2) Medium (E26) Base Lamps, 60 Watt Maximum



66742

Senecaville

1 Light Wall Lantern

Weathered Bronze Finish on Steel with White Alabaster Glass
 Height: 16.25" Width: 8" Extends: 9.5"
 Height from Center of Outlet Box: 6.5"
 Back Plate: H: 7.5" W: 6.5"
 Use (1) Medium (E26) Base Lamp, 100 Watt Maximum



66741

Senecaville

1 Light Wall Lantern

Weathered Bronze Finish on Steel with White Alabaster Glass
 Height: 13.13" Width: 6.5" Extends: 8"
 Height from Center of Outlet Box: 5.25"
 Back Plate: H: 6.13" W: 5.38"
 Use (1) Medium (E26) Base Lamp, 100 Watt Maximum



66746

Senecaville

2 Light Flush

Weathered Bronze Finish on Steel with White Alabaster Glass
 Height: 6" Diameter: 12"
 Use (2) Medium (E26) Base Lamps, 60 Watt Maximum

62308

Naveen

1 Light Wall Lantern

Oil Rubbed Bronze Finish on Steel with White Alabaster Glass
 Height: 13.63" Width: 5.5" Extends: 6.63"
 Height from Center of Outlet Box: 4.75"
 Back Plate: H: 5.88" W: 4.38"
 Use (1) Medium (E26) Base Lamp, 100 Watt Maximum



69407

Claremont

2 Light Flush

Textured Rust Patina Finish on Steel with White Alabaster Glass
 Height: 5" Diameter: 12"
 Use (2) Medium (E26) Base Lamps, 60 Watt Maximum






67864
1 Light Wall Lantern
 Textured White Finish
 on Cast Aluminum
 with Clear Curved Beveled Glass
 Height: 20" Width: 7" Extends: 9.25"
 Height from Center
 of Outlet Box: 16"
 Back Plate: H: 6.88" W: 4.38"
 Use (1) Medium (E26) Base Lamp,
 100 Watt Maximum



64683
1 Light Wall Lantern
 Textured Rust Patina Finish
 on Cast Aluminum
 with Clear Curved Beveled Glass
 Height: 20" Width: 7" Extends: 9.25"
 Height from Center
 of Outlet Box: 16"
 Back Plate: H: 6.88" W: 4.38"
 Use (1) Medium (E26) Base Lamp,
 100 Watt Maximum



67863
1 Light Wall Lantern
 Textured Black Finish
 on Cast Aluminum
 with Clear Curved Beveled Glass
 Height: 20" Width: 7" Extends: 9.25"
 Height from Center
 of Outlet Box: 16"
 Back Plate: H: 6.88" W: 4.38"
 Use (1) Medium (E26) Base Lamp,
 100 Watt Maximum



69823
Country Club
1 Light Dual Mount Pendant
 Weathered Bronze Finish
 with Clear Curved Beveled Glass
 Height: 14.25" Diameter: 7"
 Chain: 36" Wire: 120"
 Use (1) Medium (E26) Base Lamp,
 100 Watt Maximum



66924
1 Light Wall Lantern
 Polished Brass Finish
 on Steel with Clear Curved Beveled Glass
 Height: 18.5" Width: 5.75" Extends: 6"
 Height from Center of Outlet Box: 11.5"
 Back Plate: D: 4.5"
 Use (1) Medium (E26) Base Lamp,
 100 Watt Maximum

67873
1 Light Wall Lantern
 Weathered Bronze Finish
 with Clear Glass
 Height: 12" Width: 6.5" Extends: 6.5"
 Height from Center of Outlet Box: 6.5"
 Back Plate: H: 5.5" W: 4.75"
 Use (1) Medium (E26) Base Lamp,
 60 Watt Maximum



66853
1 Light Wall Lantern
 Polished Brass Finish
 on Steel with Clear Beveled Glass
 Height: 12" Width: 7" Extends: 7"
 Height from Center of Outlet Box: 2.75"
 Back Plate: H: 5.5" W: 4.75"
 Use (1) Medium (E26) Base Lamp,
 100 Watt Maximum



66832
1 Light Wall Lantern
 Weathered Bronze Finish
 on Steel with Clear Curved Beveled Glass
 Height: 15" Width: 6.5" Extends: 7"
 Height from Center of Outlet Box: 7.5"
 Back Plate: H: 5.5" W: 4.75"
 Use (1) Medium (E26) Base Lamp,
 100 Watt Maximum



66970
1 Light Wall Lantern
 Polished Brass Finish
 on Steel with Clear Curved Beveled Glass
 Height: 15" Width: 6.5" Extends: 7"
 Height from Center of Outlet Box: 7.5"
 Back Plate: H: 5.5" W: 4.75"
 Use (1) Medium (E26) Base Lamp,
 100 Watt Maximum

67492

Stanford

1 Light Wall Lantern

Auburn Patina Finish on Steel with Frosted Smoke Alabaster Glass

Height: 10.75" Width: 7" Extends: 8.87"

Height from Center of Outlet Box: 2.37"

Back Plate: H: 4.63" W: 4.38"

Use (1) Medium (E26) Base Lamp,

100 Watt Maximum



67509

Mystic Bay

1 Light Pendant

Rust Finish on Cast Aluminum with Frosted Seeded Glass

Height: 14.38" Width: 9.25"

Chain: 36" Wire: 120"

Use (1) Medium (E26) Base Lamp,

100 Watt Maximum



67519

1 Light Wall Lantern

Rust Finish on Cast Aluminum with Clear Water Glass

Height: 11.5" Square: 6" Extends: 8.25"

Height from Center of Outlet Box: 6.25"

Back Plate: H: 7.75" W: 4.5"

Use (1) Medium (E26) Base Lamp,

100 Watt Maximum



69395

Exteriore

1 Light Wall Lantern

Textured Rust Patina Finish on Cast Aluminum with Clear Seeded Glass

Height: 13.5" Width: 6.5" Extends: 7.25"

Height from Center of Outlet Box: 5"

Back Plate: H: 6.88" W: 4.5"

Use (1) Medium (E26) Base Lamp,

100 Watt Maximum



66233

Adamsville

2 Light Wall Lantern

Oil Rubbed Bronze Finish on Steel with Clear Seeded Glass

Height: 17.38" Width: 8.5" Extends: 10.87"

Height from Center of Outlet Box: 8.12"

Back Plate: H: 11.5" W: 4.25"

Use (2) Candelabra (E12) Base Lamps,

60 Watt Maximum



62306

New Haven

1 Light Wall Lantern

Oil Rubbed Bronze Finish on Steel with Clear Seeded Glass

Height: 12.75" Width: 6.5" Extends: 8.63"

Height from Center of Outlet Box: 4.88"

Back Plate: D: 4.75"

Use (1) Medium (E26) Base Lamp,

100 Watt Maximum



67904

Olde Town

1 Light Wall Lantern

Burnt Sienna Finish on Aluminum with Clear Seeded Glass

Height: 17.5" Width: 6.5"

Extends: 6.5"

Height from Center

of Outlet Box: 7.63"

Back Plate: H: 7" W: 4.63"

Use (1) Medium (E26) Base Lamp,

100 Watt Maximum



67905

Olde Town

1 Light Dual Mount Pendant

Burnt Sienna Finish on Aluminum with Clear Seeded Glass

Height: 16" Width: 6.5"

Chain: 36" Wire: 120"

Use (1) Medium (E26) Base Lamp,

100 Watt Maximum



67850

1 Light Wall Lantern

*Antique Silver Finish
on Cast Aluminum with Clear Water Glass
Height: 15.75" Width: 6" Extends: 6.75"
Height from Center of Outlet Box: 4"
Back Plate: H: 5.88" W: 4.5"
Use (1) Medium (E26) Base Lamp,
100 Watt Maximum*



67851

1 Light Wall Lantern

*Textured Rust Patina Finish
on Cast Aluminum with Clear Water Glass
Height: 15.75" Width: 6" Extends: 6.75"
Height from Center of Outlet Box: 4"
Back Plate: H: 5.88" W: 4.5"
Use (1) Medium (E26) Base Lamp,
100 Watt Maximum*



67843

1 Light Pendant

*Textured Black Finish
on Cast Aluminum with Clear Glass
Height: 12.25" Width: 8" Chain: 36" Wire: 120"
Use (1) Medium (E26) Base Lamp, 100 Watt Maximum*

67846

1 Light Wall Lantern

*Textured Black Finish
on Cast Aluminum with Clear Glass
Height: 12.5" Width: 7" Extends: 9.75"
Height from Center
of Outlet Box: 3.75"
Back Plate: H: 7.88" W: 4.63"
Use (1) Medium (E26) Base Lamp,
100 Watt Maximum*



67847

1 Light Wall Lantern

*Textured White Finish
on Cast Aluminum with Clear Glass
Height: 12.5" Width: 7" Extends: 9.75"
Height from Center
of Outlet Box: 3.75"
Back Plate: H: 7.88" W: 4.63"
Use (1) Medium (E26) Base Lamp,
100 Watt Maximum*



67834

1 Light Wall Lantern

*Textured White Finish
on Cast Aluminum with
Clear Beveled Glass
Height: 11.75" Width: 6.5"
Extends: 7.75"
Height from Center
of Outlet Box: 2.75"
Back Plate: H: 5.75" W: 4.38"
Use (1) Medium
(E26) Base Lamp,
100 Watt Maximum*



67831

1 Light Wall Lantern

*Textured Black Finish
on Cast Aluminum with
Clear Beveled Glass
Height: 11.75" Width: 6.5"
Extends: 7.75"
Height from Center
of Outlet Box: 2.75"
Back Plate: H: 5.75" W: 4.38"
Use (1) Medium
(E26) Base Lamp,
100 Watt Maximum*



66828

1 Light Wall Lantern

*Textured White Finish
on Cast Aluminum with
Frosted Glass
Height: 15" Width: 6.5"
Extends: 8.12"
Height from Center
of Outlet Box: 11.5"
Back Plate: H: 5.75" W: 4.38"
Use (1) Medium
(E26) Base Lamp,
100 Watt Maximum*



66826

1 Light Wall Lantern

*Textured Black Finish
on Cast Aluminum with
Frosted Glass
Height: 15" Width: 6.5"
Extends: 8.12"
Height from Center
of Outlet Box: 11.5"
Back Plate: H: 5.75" W: 4.38"
Use (1) Medium
(E26) Base Lamp,
100 Watt Maximum*



69919
1 Light Wall Lantern
 Brushed Nickel Finish
 on Steel with Clear Textured Glass
 Height: 12" Width: 6.25" Extends: 7.25"
 Height from Center of Outlet Box: 7"
 Back Plate: H: 6.13" W: 4.38"
 Use (1) Medium (E26) Base Lamp,
 100 Watt Maximum



67930
1 Light Wall Lantern
 Bronze Patina Finish
 on Steel with Clear Textured Glass
 Height: 12" Width: 6.25" Extends: 7.25"
 Height from Center of Outlet Box: 7"
 Back Plate: H: 6.13" W: 4.38"
 Use (1) Medium (E26) Base Lamp,
 100 Watt Maximum



67518
1 Light Wall Lantern
 Rust Finish
 on Cast Aluminum with Tiffany Art Glass
 Height: 12.25" Square: 5.75" Extends: 7.5"
 Height from Center of Outlet Box: 6.25"
 Back Plate: H: 8.13" W: 4.5"
 Use (1) Medium (E26) Base Lamp,
 100 Watt Maximum



67328
Burnham
1 Light Wall Lantern
 Oil Rubbed Bronze Finish
 on Steel with Honey Art Glass
 Height: 12.5" Width: 6" Extends: 9"
 Height from Center of Outlet Box: 2.5"
 Back Plate: H: 5" W: 5"
 Use (1) Medium (E26) Base Lamp,
 100 Watt Maximum



66898
1 Light Wall Lantern
 Textured Black Finish
 on Cast Aluminum with White Acrylic Lens
 Height: 9.88" Width: 7.75" Extends: 4.13"
 Height from Center of Outlet Box: 4.25"
 Back Plate: H: 9.38" W: 7"
 Use (1) Medium (E26) Base Lamp,
 60 Watt Maximum



64829
Nova Scotia
1 Light Wall Lantern with Dusk to Dawn Sensor
 Textured Black Finish
 on Steel with Honey Art Glass
 Height: 11" Width: 6.25" Extends: 8.87"
 Height from Center of Outlet Box: 4.5"
 Back Plate: H: 8.5" W: 4"
 Use (1) GU24 Base CFL Twist Lamp,
 13 Watt, Lamp Included



66748
Moncove
1 Light Wall Lantern
 Textured Rust Patina Finish
 on Steel with Tiffany Art Glass
 Height: 12.63" Width: 8.75" Extends: 10.25"
 Height from Center of Outlet Box: 7.5"
 Back Plate: H: 8.63" W: 6.38"
 Use (1) Medium (E26) Base Lamp,
 100 Watt Maximum



64830
Nova Scotia
1 Light Wall Lantern with Dusk to Dawn Sensor
 Textured Black Finish
 on Steel with Honey Art Glass
 Height: 14.75" Width: 9.5" Extends: 13"
 Height from Center of Outlet Box: 6"
 Back Plate: H: 9.5" W: 4.5"
 Use (1) GU24 Base CFL Twist Lamp,
 23 Watt, Lamp Included



Compact Fluorescent Lamps contain mercury. For more on clean up and safe disposal, visit epa.gov/cfl.



69610

1 Light Wall Lantern

*Pewter Patina Finish
on Steel with Ice Glass*

Height: 10.75" Width: 4.5" Extends: 5"

Height from Center of Outlet Box: 4"

Back Plate: D: 4.5"

*Use (1) Medium (E26) Base Lamp,
100 Watt Maximum*



64681

1 Light Wall Lantern

*Textured Rust Patina Finish
on Steel with Ice Glass*

Height: 10.75" Width: 4.5" Extends: 5"

Height from Center of Outlet Box: 4"

Back Plate: D: 4.5"

*Use (1) Medium (E26) Base Lamp,
100 Watt Maximum*



64883

**1 Light Wall Lantern with
Dusk to Dawn Sensor**

Sienna Finish on Steel with Frosted Glass

Height: 8.25" Width: 4.5" Extends: 5.75"

Height from Center of Outlet Box: 3"

Back Plate: D: 4.5"

*Use (1) GU24 Base CFL Twist Lamp,
13 Watt, Lamp Included*



66972

1 Light Wall Lantern

*Textured Black Finish
on Steel with Clear Glass*

Height: 8.25" Width: 4.5"

Extends: 5.75"

Height from Center

of Outlet Box: 3"

Back Plate: D: 4.5"

*Use (1) Medium
(E26) Base Lamp,
100 Watt Maximum*



64684

1 Light Wall Lantern

*Antique Silver Finish
on Steel with Clear Glass*

Height: 8.25" Width: 4.5"

Extends: 5.75"

Height from Center

of Outlet Box: 3"

Back Plate: D: 4.5"

*Use (1) Medium
(E26) Base Lamp,
100 Watt Maximum*



66935

1 Light Wall Lantern

*Sienna Finish
on Steel with Clear Glass*

Height: 8.25" Width: 4.5"

Extends: 5.75"

Height from Center

of Outlet Box: 3"

Back Plate: D: 4.5"

*Use (1) Medium
(E26) Base Lamp,
100 Watt Maximum*



66937

1 Light Wall Lantern

*Antique Brass Finish
on Steel with Clear Glass*

Height: 8.25" Width: 4.5"

Extends: 5.75"

Height from Center

of Outlet Box: 3"

Back Plate: D: 4.5"

*Use (1) Medium
(E26) Base Lamp,
100 Watt Maximum*



66936

1 Light Wall Lantern

*Polished Brass Finish
on Steel with Clear Glass*

Height: 8.25" Width: 4.5"

Extends: 5.75"

Height from Center of Outlet Box: 3"

Back Plate: D: 4.5"

*Use (1) Medium (E26) Base Lamp,
100 Watt Maximum*



66971

1 Light Wall Lantern

*White Finish
on Steel with Clear Glass*

Height: 8.25" Width: 4.5"

Extends: 5.75"

Height from Center of Outlet Box: 3"

Back Plate: D: 4.5"

*Use (1) Medium (E26) Base Lamp,
100 Watt Maximum*



66938

1 Light Wall Lantern

*Goldenrod Finish
on Steel with Clear Glass*


Height: 8.25" Width: 4.5"

Extends: 5.75"

Height from Center of Outlet Box: 3"

Back Plate: D: 4.5"

*Use (1) Medium (E26) Base Lamp,
100 Watt Maximum*

Compact Fluorescent Lamps contain mercury.  For more on clean up and safe disposal, visit epa.gov/cfl.



64516
1 Light Wall Lantern with Dusk to Dawn Sensor

*Matte Black Finish on Steel
 with Frosted Curved Glass
 Height: 7.75" Width: 6" Extends: 6.5"
 Height from Center of Outlet Box: 2.25"
 Back Plate: D: 4.5"
 Use (1) GU24 Base CFL Twist Lamp,
 13 Watt, Lamp Included*



64688
1 Light Wall Lantern

*Antique Silver Finish on Steel
 with Clear Curved Glass
 Height: 7.75" Width: 6" Extends: 6.5"
 Height from Center of Outlet Box: 2.25"
 Back Plate: D: 4.5"
 Use (1) Medium (E26) Base Lamp,
 100 Watt Maximum*



64689
1 Light Wall Lantern

*Textured Rust Patina Finish on Steel
 with Clear Curved Glass
 Height: 7.75" Width: 6" Extends: 6.5"
 Height from Center of Outlet Box: 2.25"
 Back Plate: D: 4.5"
 Use (1) Medium (E26) Base Lamp,
 100 Watt Maximum*



66961
1 Light Wall Lantern

*Matte Black Finish on Steel
 with Clear Curved Glass
 Height: 7.75" Width: 6" Extends: 6.5"
 Height from Center of Outlet Box: 2.25"
 Back Plate: D: 4.5"
 Use (1) Medium (E26) Base Lamp,
 100 Watt Maximum*



66962
1 Light Wall Lantern

*White Finish on Steel
 with Clear Curved Glass
 Height: 7.75" Width: 6" Extends: 6.5"
 Height from Center of Outlet Box: 2.25"
 Back Plate: D: 4.5"
 Use (1) Medium (E26) Base Lamp,
 100 Watt Maximum*



67963
1 Light Wall Lantern

*Polished Brass Finish on Steel
 with Clear Curved Glass
 Height: 7.75" Width: 6" Extends: 6.5"
 Height from Center of Outlet Box: 2.25"
 Back Plate: D: 4.5"
 Use (1) Medium (E26) Base Lamp,
 100 Watt Maximum*

Compact Fluorescent Lamps contain mercury. For more on clean up and safe disposal, visit epa.gov/cfl.

**64686****1 Light Wall Lantern***Antique Silver Finish
on Steel with Clear Glass**Height: 13.5" Width: 4.75"**Extends: 5.75"**Height from Center of Outlet Box: 8"**Back Plate: D: 4.5"**Use (1) Medium (E26) Base Lamp,
100 Watt Maximum***67887****1 Light Wall Lantern***White Finish on Steel
with Polished Brass Accents
with Clear Beveled Glass**Height: 14.25" Width: 5.25"**Extends: 6"**Height from Center of Outlet Box: 8.5"**Back Plate: D: 4.5"**Use (1) Medium (E26) Base Lamp,
100 Watt Maximum***64687****1 Light Wall Lantern***Textured Rust Patina Finish
on Steel with Clear Glass**Height: 13.5" Width: 4.75"**Extends: 5.75"**Height from Center of Outlet Box: 8"**Back Plate: D: 4.5"**Use (1) Medium (E26) Base Lamp,
100 Watt Maximum***66963****1 Light Wall Lantern***Antique Brass Finish
on Steel with Clear Glass**Height: 13.5" Width: 4.75"**Extends: 5.75"**Height from Center of Outlet Box: 8"**Back Plate: D: 4.5"**Use (1) Medium (E26) Base Lamp,
100 Watt Maximum***66984****1 Light Wall Lantern***White Finish
on Steel with Clear Glass**Height: 13.5" Width: 4.75"**Extends: 5.75"**Height from Center of Outlet Box: 8"**Back Plate: D: 4.5"**Use (1) Medium (E26) Base Lamp,
100 Watt Maximum***66983****1 Light Wall Lantern***Matte Black Finish
on Steel with Clear Glass**Height: 13.5" Width: 4.75"**Extends: 5.75"**Height from Center of Outlet Box: 8"**Back Plate: D: 4.5"**Use (1) Medium (E26) Base Lamp,
100 Watt Maximum***66964****1 Light Wall Lantern***Polished Brass Finish
on Steel with Clear Glass**Height: 13.5" Width: 4.75"**Extends: 5.75"**Height from Center of Outlet Box: 8"**Back Plate: D: 4.5"**Use (1) Medium (E26) Base Lamp,
100 Watt Maximum*

67836

1 Light Wall Fixture

White Finish on Steel with White Glass Lens
 Diameter: 8" Extends: 4"
 Use (1) Medium (E26)
 Base Lamp, 60 Watt Maximum



67835

1 Light Wall Fixture

White Finish on Steel with White Glass Lens
 Height: 4.25" Width: 8.5"
 Extends: 4"
 Use (1) Medium (E26)
 Base Lamp, 60 Watt Maximum.



66881

1 Light Wall Lantern

Textured Black Finish on Cast Aluminum with Frosted Glass
 Height: 8.5" Width: 6"
 Extends: 6.75"
 Height from Center of Outlet Box: 3.88"
 Back Plate: D: 4.75"
 Use (1) Medium (E26) Base Lamp, 60 Watt Maximum



66879

1 Light Wall Lantern

Textured White Finish on Cast Aluminum with Frosted Glass
 Height: 8.5" Width: 6"
 Extends: 6.75"
 Height from Center of Outlet Box: 3.88"
 Back Plate: D: 4.75"
 Use (1) Medium (E26) Base Lamp, 60 Watt Maximum



67975

2 Light Wall Fixture

Polished Graphite Finish on Steel Cylinder
 Height: 15" Width: 5"
 Extends: 8.25"
 Height from Center of Outlet Box: 7.5"
 Back Plate: H: 5" W: 4.25"
 Use (2) Medium (E26)
 Base Lamps, 75 Watt Maximum



67973

1 Light Wall Fixture

Polished Graphite Finish on Steel Cylinder
 Height: 7" Width: 4.5"
 Extends: 7.87"
 Height from Center of Outlet Box: 2.76"
 Back Plate: H: 5" W: 4.25"
 Use (1) Medium (E26)
 Base Lamp, 75 Watt Maximum



66955

Lantern Post with Ground Convenience Outlet & Dusk to Dawn Sensor

Black Finish on Steel
 Height: 84" Diameter: 3"
 (Includes ladder rest)



66808

Lantern Post

Black Finish on Steel
 Height: 84" Diameter: 3"
 (Includes ladder rest)

66991

Steel Ladder Rest and Polycarbonate Spherettes

Black Finish
 Diameter: 1.38" Width: 15.75"



67901

Pedestal Mount for Post Lantern

Textured Black Finish
 Height: 3.13" Square: 5.63"
 3" Diameter Pedestal Mount



67978

1 Light Wall Lantern

Brushed Aluminum Finish on Cast Aluminum with White Threaded Glass Globe

Height: 7" Diameter: 5.75" Extends: 7"

Height from Center of Outlet Box: 3.25"

Back Plate: H: 5.88" W: 4.5"

Use (1) Medium (E26) Base Lamp, 100 Watt Maximum



67980

1 Light Flush

Brushed Aluminum Finish on Cast Aluminum with White Glass Globe

Height: 7.25" Diameter: 6"

Use (1) Medium (E26) Base Lamp,

60 Watt Maximum

66840

1 Light Flush

Black Finish on Steel with White Glass Globe

Height: 7.25" Diameter: 6"

Use (1) Medium (E26) Base Lamp,

60 Watt Maximum



66945

1 Light Hi-Impact Polycarbonate Wall Lantern

White Finish with White Glass Globe

Height: 7.25" Diameter: 6" Extends: 7"

Height from Center of Outlet Box: 2.5"

Back Plate: H: 4.38" W: 4.5"

Use (1) Medium (E26) Base Lamp,

60 Watt Maximum



66803

1 Light Hi-Impact Polycarbonate Wall Lantern

Black Finish with White Glass Globe

Height: 7.25" Diameter: 6" Extends: 7"

Height from Center of Outlet Box: 2.5"

Back Plate: H: 4.38" W: 4.5"

Use (1) Medium (E26) Base Lamp,

60 Watt Maximum



66861

1 Light Polycarbonate Post Top Lantern

Black Finish with White Acrylic Globe

Height: 13" Diameter: 12"

Use (1) Medium (E26) Base Lamp,

100 Watt Maximum

(Fits standard 3" post, post sold separately)



66878
1 Light Wall Lantern

*White Finish
 on Steel with Clear Glass*
 Height: 7.5" Diameter: 4.5" Extends: 5.75"
 Height from Center of Outlet Box: 2"
 Back Plate: D: 4.5"
 Use (1) Medium (E26) Base Lamp,
 100 Watt Maximum



66885
1 Light Wall Lantern

*Matte Black Finish
 on Steel with Clear Glass*
 Height: 7.5" Diameter: 4.5" Extends: 5.75"
 Height from Center of Outlet Box: 2"
 Back Plate: D: 4.5"
 Use (1) Medium (E26) Base Lamp,
 100 Watt Maximum



66884
1 Light Wall Lantern

*Polished Brass Finish
 on Steel with Clear Glass*
 Height: 7.5" Diameter: 4.5" Extends: 5.75"
 Height from Center of Outlet Box: 2"
 Back Plate: D: 4.5"
 Use (1) Medium (E26) Base Lamp,
 100 Watt Maximum



66839
1 Light Wall Lantern

*Antique Brass Finish
 on Steel with Clear Glass*
 Height: 7.5" Diameter: 4.5" Extends: 5.75"
 Height from Center of Outlet Box: 2"
 Back Plate: D: 4.5"
 Use (1) Medium (E26) Base Lamp,
 100 Watt Maximum



66818
1 Light Flush

*Antique Brass Finish
 on Steel with Clear Glass*
 Height: 6" Diameter: 4.75"
 Use (1) Medium (E26) Base Lamp,
 60 Watt Maximum



66919
1 Light Flush

*Matte Black Finish
 on Steel with Clear Glass*
 Height: 6" Diameter: 4.75"
 Use (1) Medium (E26) Base Lamp,
 60 Watt Maximum



66800
**1 Light Hi-Impact Polypropylene
 Wall Lantern**

Black Finish with Clear Glass
 Height: 6" Diameter: 4.5"
 Extends: 5.75"
 Height from Center of Outlet Box: 2.5"
 Back Plate: H: 4.38" W: 4.5"
 Use (1) Medium (E26) Base Lamp,
 60 Watt Maximum



66949
**1 Light Hi-Impact Polycarbonate
 Wall Lantern with Dusk to Dawn Sensor**

Black Finish with Clear Glass
 Height: 6" Diameter: 4.5"
 Extends: 5.75"
 Height from Center of Outlet Box: 2.5"
 Back Plate: H: 4.38" W: 4.5"
 Use (1) Medium (E26) Base Lamp,
 60 Watt Maximum



66946
1 Light Hi-Impact Polycarbonate Wall Lantern with Removable Tail
White Finish with Clear Textured Acrylic
 Height with Tail: 17" Height without Tail: 13"
 Square: 8" Extends: 8.5"
 Height from Center of Outlet Box: 10.75"
 Back Plate: H: 4.63" W: 4.63"
 Use (1) Medium (E26) Base Lamp,
 60 Watt Maximum


66859
1 Light Hi-Impact Polypropylene Wall Lantern
Black Finish with Clear Textured Acrylic
 Height: 8" Width: 7.25" Extends: 6"
 Height from Center of Outlet Box: 2.37"
 Back Plate: D: 4.75"
 Use (1) Medium (E26) Base Lamp,
 60 Watt Maximum



66860
1 Light Hi-Impact Polycarbonate Wall Lantern with Removable Tail
Black Finish with Clear Textured Acrylic
 Height with Tail: 17" Height without Tail: 13"
 Square: 8" Extends: 8.5"
 Height from Center of Outlet Box: 10.75"
 Back Plate: H: 4.63" W: 4.63"
 Use (1) Medium (E26) Base Lamp,
 60 Watt Maximum



66822
1 Light Hi-Impact Polypropylene Flush
Black Finish with Clear Textured Glass
 Height: 4.75" Square: 8.25"
 Use (1) Medium (E26) Base Lamp,
 60 Watt Maximum



66823
2 Light Hi-Impact Polypropylene Flush
Black Finish with Clear Textured Glass Panels
 Height: 5.5" Square: 10.25"
 Use (2) Medium (E26) Base Lamps,
 60 Watt Maximum



66975
1 Light Hi-Impact Polypropylene Flush
White Finish with Clear Textured Glass Panels
 Height: 4.75" Square: 8.25"
 Use (1) Medium (E26) Base Lamp,
 60 Watt Maximum



66976
2 Light Hi-Impact Polypropylene Flush
White Finish with Clear Textured Glass Panels
 Height: 5.5" Square: 10.25"
 Use (2) Medium (E26) Base Lamps,
 60 Watt Maximum

66875
1 Light Hi-Impact Polycarbonate Post Top Lantern
Black Finish with Clear Textured Acrylic Panels
 Height: 12.38" Square: 8"
 Use (1) Medium (E26) Base Lamp,
 60 Watt Maximum
 (Fits standard 3" post,
 post sold separately)





ACCENT LIGHTING

picture lights...

Picture lights amplify the natural beauty of treasured artwork and photographs and provide light where it's needed most.




Slimline Picture Lights


Picture lights include:


- Adjustable neck and shade
- 8' cord set
- In-line on/off switch
- Detachable polarized plug
- Mounting hardware
- Westinghouse lamps



75051
14" Picture Light
 Polished Brass Finish 
 Extends 6" From Wall
 Includes (2) T6, 15 Watt
 Frost Lamps



75053
14" Picture Light
 Antique Brass Finish 
 Extends 6" From Wall
 Includes (2) T6, 15 Watt
 Frost Lamps



75052
7" Picture Light
 Antique Brass Finish 
 Extends 5 7/8" From Wall
 Includes (1) T6, 15 Watt
 Frost Lamp



75050
7" Picture Light
 Polished Brass Finish 
 Extends 5 7/8" From Wall
 Includes (1) T6, 15 Watt
 Frost Lamp

CEILING FANS

LOW CEILINGS



Install hugger ceiling fans or ceiling fans without a down rod in rooms with low ceilings.

STANDARD 8 FT. CEILINGS



Install ceiling fans with or without a down rod in rooms with standard 8' ceilings. See page 124 to view our full assortment of extension down rods.

SELECT THE RIGHT SIZE CEILING FAN FOR EVERY ROOM

Maximize air flow by installing an appropriately sized ceiling fan for your room.

For rooms up to 8' x 10' Use 24" - 42" ceiling fans.

For rooms up to 12' x 12' Use 42" - 48" ceiling fans.

For rooms up to 18' x 20' Use ceiling fans 50" and larger.



Westinghouse

INNOVATION YOU CAN BE SURE OF



All ceiling fans in this catalog are UL or ETL Listed.

Fashionable, high quality ceiling fans and light kits add comfort, color and complementary style to any room. A trusted name for over 120 years, Westinghouse guarantees the construction of its ceiling fans with a limited lifetime warranty. Westinghouse... Innovation you can be sure of.

HIGH AND SLOPED CEILINGS



Install ceiling fans with extension down rods in rooms with high and sloped ceilings. See page 124-125 for a full assortment of extension down rods and ceiling fan controls.

INDOOR / OUTDOOR



In outdoor areas, install ceiling fans that are approved for use in damp or wet locations. See pages 114-116 to view our indoor/outdoor assortment.

YEAR-ROUND COMFORT & EFFICIENCY



For year-round comfort and maximum energy savings, Westinghouse ceiling fans include a reversible switch that allows the ceiling fans to be used during cool or warm weather. In the summer, keep your home cool by running your ceiling fan counterclockwise. In the winter, run your ceiling fan clockwise to re-circulate warm air from the ceiling, eliminating cold spots and drafts.



CONTEMPORARY

ceiling fan collection...

Featuring a wide range of modern and transitional styles, our contemporary collection of ceiling fans captures the essence of today's lifestyle trends through modern designs and fashion-forward finishes.



52" Delancey



78001

52" Brushed Chrome Finish

Silver ABS Blades
Includes Light Fixture
with Opal Frosted Glass



SPECIFICATIONS

- Limited Lifetime Warranty
 - DC Motor 125S
 - 13° Blade Pitch
 - ¾" x 4" Down Rod
 - 78" Lead Wire
 - Includes Remote Control
 - Includes: (2) Medium Base, 13 Watt CFL Mini-Twists
- Airflow:** 5722 Cubic Feet Per Minute
Electricity Use: 32 Watts (excludes lights)
Airflow Efficiency: 178 Cubic Feet Per Minute Per Watt

SPECIFICATIONS

- Limited Lifetime Warranty
 - Silicon Steel Motor 153mm X 17mm
 - 13° Blade Pitch
 - ¾" x 4" Down Rod
 - 78" Lead Wire
 - Includes Remote Control
 - Includes: (1) 17 Watt Integrated LED Light Source, Average Rated Hours: 25,000
- Airflow:** 4264 Cubic Feet Per Minute
Electricity Use: 52 Watts (excludes lights)
Airflow Efficiency: 82 Cubic Feet Per Minute Per Watt



52" Techno

78002

52" Brushed Aluminum Finish

Gray ABS Blades
Includes Light Fixture
with Opal Frosted Glass

52" Bendan



72557

52" Satin Chrome Finish

Wengue Plywood Blades
Includes Light Fixture
with Opal Frosted Glass

SPECIFICATIONS

- Limited Lifetime Warranty
 - Cold Rolled Steel Motor 153mm X 18mm
 - 12° Blade Pitch
 - ¾" x 4" Down Rod
 - 78" Lead Wire
 - Includes Remote Control
 - Includes: (1) R7 Base, 100 Watt Halogen Lamp
- Airflow:** 4739 Cubic Feet Per Minute
Electricity Use: 60 Watts (excludes lights)
Airflow Efficiency: 79 Cubic Feet Per Minute Per Watt

Compact Fluorescent Lamps contain mercury. For more on clean up and safe disposal, visit epa.gov/cfl.

24" Quince Collection



78631
24" Chrome Finish
 Reversible Blades (Wengue/Beech)
 Includes Light Fixture with Opal Frosted Glass



72243
24" Gun Metal Finish
 Reversible Blades (Black/Graphite)
 Includes Light Fixture with Opal Frosted Glass



SPECIFICATIONS

- Limited Lifetime Warranty
- Silicon Steel Motor 153mm X 9mm
- 18° Blade Pitch
- 3/4" x 4" Down Rod
- 78" Lead Wire
- Includes: (2) Candelabra Base, 40 Watt G16 1/2 Lamps

Airflow: 2039 Cubic Feet Per Minute
Electricity Use: 31 Watts (excludes lights)
Airflow Efficiency: 67 Cubic Feet Per Minute Per Watt

72471
24" White Finish
 Reversible Blades (White/Beech)
 Includes Light Fixture with Opal Frosted Glass

24" Origami Collection



78644
24" Chrome Finish
 Reversible Blades (Wengue/Beech)
 Includes Light Fixture with Opal Frosted Glass



72229
24" Espresso Finish
 Reversible Blades (Espresso/Applewood)
 Includes Light Fixture with Opal Frosted Glass

SPECIFICATIONS

- Limited Lifetime Warranty
- Silicon Steel Motor 153mm X 9mm
- 18° Blade Pitch
- 3/4" x 4" Down Rod
- 78" Lead Wire
- Includes: (1) Candelabra Base, 60 Watt G16 1/2 Lamp

Airflow: 2039 Cubic Feet Per Minute
Electricity Use: 31 Watts (excludes lights)
Airflow Efficiency: 66 Cubic Feet Per Minute Per Watt

30" Wengue Collection

SPECIFICATIONS

- Limited Lifetime Warranty
- Silicon Steel Motor 153mm X 9mm
- 18° Blade Pitch
- ¾" x 4" Down Rod
- 78" Lead Wire
- Includes: (2) Candelabra Base, 40 Watt G16 1/2 Lamps

Airflow: 2543 Cubic Feet Per Minute

Electricity Use: 39 Watts (excludes lights)

Airflow Efficiency: 65 Cubic Feet Per Minute Per Watt



72472

30" White Finish

Reversible Blades (White/Beech)

Includes Light Fixture with Opal Frosted Glass



78763

30" Chrome Finish

Reversible Blades

(Wengue/Beech)

Includes Light Fixture with Opal Frosted Glass



72245

30" Espresso Finish

Reversible Blades

(Espresso/Dark Cherry)

Includes Light Fixture with Opal Frosted Glass



72475

30" Brushed Nickel Finish

Reversible MDF Blades (Multi-Color/White)

Includes Opal Frosted Glass Light Fixture



30" Roundabout

SPECIFICATIONS

- Limited Lifetime Warranty
- Silicon Steel Motor 153mm X 10mm
- 18° Blade Pitch
- ¾" x 4" Down Rod
- 78" Lead Wire
- Includes: (2) Candelabra Base, 40 Watt G16 1/2 Lamps

Airflow: 2483 Cubic Feet Per Minute

Electricity Use: 39 Watts (excludes lights)

Airflow Efficiency: 63 Cubic Feet Per Minute Per Watt

30" Turbo Swirl Collection

7814465

30" Brushed Aluminum Finish

*Light Maple Blades
Includes Light Fixture
with Opal Frosted Glass*



SPECIFICATIONS

- Limited Lifetime Warranty
 - Silicon Steel Motor 153mm X 10mm
 - 18° Blade Pitch
 - ¾" x 4" Down Rod
 - 78" Lead Wire
 - Includes: (1) Candelabra Base, 60 Watt G16 1/2 Lamp
- Airflow:** 2541 Cubic Feet Per Minute
Electricity Use: 45 Watts (excludes lights)
Airflow Efficiency: 57 Cubic Feet Per Minute Per Watt



7814565

30" White Finish

*White Blades
Includes Light Fixture
with Opal Frosted Glass*



7824865

30" Antique Brass

*Walnut Blades
Includes Light Fixture
with Opal Frosted Glass*

30" Turbo Swirl CFL

SPECIFICATIONS

- Limited Lifetime Warranty
 - Cold Rolled Steel Motor 153mm X 12mm
 - 18° Blade Pitch
 - ¾" x 4" Down Rod
 - 78" Lead Wire
 - Includes: (1) Medium Base, 13 Watt CFL Mini-Twist
- Airflow:** 3519 Cubic Feet Per Minute
Electricity Use: 50 Watts (excludes lights)
Airflow Efficiency: 70 Cubic Feet Per Minute Per Watt



72261

30" Gun Metal Finish

*Black Blades
Includes Light Fixture with Opal Frosted Glass*

Compact Fluorescent Lamps contain mercury. (Hg) For more on clean up and safe disposal, visit epa.gov/cfl.

42" Alloy Collection



78764
42" Gun Metal Finish
Reversible Blades (Black/Graphite)
Includes Light Fixture with Opal Frosted Glass

SPECIFICATIONS

- Limited Lifetime Warranty
 - Silicon Steel Motor 153mm X 10mm
 - 12° Blade Pitch
 - 3/4" x 4" Down Rod
 - 78" Lead Wire
 - Includes: (2) Candelabra Base, 40 Watt G16 1/2 Lamps
- Airflow:** 4083 Cubic Feet Per Minute
Electricity Use: 51 Watts (excludes lights)
Airflow Efficiency: 80 Cubic Feet Per Minute Per Watt



72473
42" Brushed Nickel Finish
Reversible Blades (Beech/Wengue)
Includes Light Fixture with Opal Frosted Glass

48" Cumulus

SPECIFICATIONS

- Limited Lifetime Warranty
 - Silicone Steel Motor 153mm X 15mm
 - 12° Blade Pitch
 - 3/4" x 10" Down Rod
 - 78" Lead Wire
 - Includes Remote Control
 - Includes: (1) E11 Mini-Can Base, 75 Watt Maximum
- Airflow:** 4592 Cubic Feet Per Minute
Electricity Use: 53 Watts (excludes lights)
Airflow Efficiency: 87 Cubic Feet Per Minute Per Watt



72598
48" White Finish
Reversible Blades (White/White Washed Pine)
Includes Light Fixture with Opal Frosted Glass

78775

46" Brushed Nickel Finish

*Reversible Plywood Blades
(Beech/Weathered Maple)
Includes Light Fixture with
Frosted White Alabaster Glass*



46" Arcadia Collection



78691

46" White Finish

*Reversible Plywood Blades
(Light Maple/White)
Includes Light Fixture with
Frosted White Alabaster Glass*

SPECIFICATIONS

- Limited Lifetime Warranty
 - Silicon Steel Motor 153mm X 12mm
 - 12° Blade Pitch
 - 3/4" x 4" Down Rod
 - 78" Lead Wire
 - Includes Remote Control
 - Includes: (2) Candelabra Base, 40 Watt G16 1/2 Lamps
- Airflow:** 4300 Cubic Feet Per Minute
Electricity Use: 52 Watts (excludes lights)
Airflow Efficiency: 82 Cubic Feet Per Minute Per Watt.

48" Lavada



SPECIFICATIONS

- Limited Lifetime Warranty
 - Silicon Steel Motor 153mm X 15mm
 - 12° Blade Pitch
 - 3/4" x 4" Down Rod
 - 78" Lead Wire
 - Includes: (1) R7 Base, 100 Watt Halogen Lamp
- Airflow:** 4757 Cubic Feet Per Minute
Electricity Use: 52 Watts (excludes lights)
Airflow Efficiency: 91 Cubic Feet Per Minute Per Watt

72474

48" Brushed Nickel Finish

*Reversible Plywood Blades
(Dark Cherry/Applewood)
Includes Light Fixture
with Frosted Opal Glass*

48" Solana

SPECIFICATIONS

- Limited Lifetime Warranty
 - Silicon Steel Motor 153mm X 17mm
 - 12° Blade Pitch
 - 3/4" x 4" Down Rod
 - 78" Lead Wire
 - Includes Remote Control
 - Includes: (2) Candelabra Base, 60 Watt G16 1/2 Lamps
- Airflow:** 3313 Cubic Feet Per Minute
Electricity Use: 49 Watts (excludes lights)
Airflow Efficiency: 68 Cubic Feet Per Minute Per Watt



72161

48" Brushed Nickel Finish

Wengue Plywood Blades

Includes Light Fixture with Opal Frosted Glass

48" Harmony

SPECIFICATIONS

- Limited Lifetime Warranty
 - Silicon Steel Motor 153mm X 20mm
 - 13° Blade Pitch
 - 3/4" x 6" Down Rod
 - 78" Lead Wire
 - 4-Speed Fan Control
 - Includes: (2) Candelabra Base, 40 Watt Torpedo Lamps
- Airflow:** 4881 Cubic Feet Per Minute
Electricity Use: 53 Watts (excludes lights)
Airflow Efficiency: 92 Cubic Feet Per Minute Per Watt



72141

48" Brushed Nickel Finish

Weathered Maple Plywood Blades

Includes Light Fixture with Opal Frosted Glass

52" Sparta

78524

52" Brushed Nickel Finish

Weathered Maple Plywood Blades
Includes Light Fixture
with Opal Glass



SPECIFICATIONS

- Limited Lifetime Warranty
 - Silicon Steel Motor 153mm X 15mm
 - 13° Blade Pitch
 - 3/4" x 4" Down Rod
 - 54" Lead Wire
 - Includes Remote Control
 - Includes: (1) E11 Base, 100 Watt Single-Ended Halogen
- Airflow:** 5017 Cubic Feet Per Minute
Electricity Use: 54 Watts (excludes lights)
Airflow Efficiency: 93 Cubic Feet Per Minute Per Watt

52" Comet Collection



7813665

52" Brushed Pewter Finish

*Reversible Plywood Blades (Light Maple/White)
Includes Light Fixture with Frosted Glass*

SPECIFICATIONS

- Limited Lifetime Warranty
 - Cold Rolled Steel Motor 153mm X 15mm
 - 11° Blade Pitch
 - ¾" x 4" Down Rod
 - 78" Lead Wire
 - Includes: (2) Candelabra Base, 40 Watt Torpedo Lamps
- Airflow:** 5199 Cubic Feet Per Minute Electricity
Electricity Use: 61 Watts (excludes lights)
Airflow Efficiency: 85 Cubic Feet Per Minute Per Watt.



7801765

52" White Finish

*Reversible Plywood Blades
(White/White Washed Pine)
Includes Light Fixture with Frosted Glass*



7801665

52" Matte Black Finish

*Reversible Plywood Blades
(Matte Black/Marble)
Includes Light Fixture
with Frosted Glass*

42" Vector Elite



78507
42" Brushed Nickel and Graphite Finish
Reversible Plywood Blades (Graphite/Silver)
Includes Light Fixture with Brushed Nickel Spot Lights

SPECIFICATIONS

- Limited Lifetime Warranty
 - Silicon Steel Motor 153mm X 10mm
 - 16° Blade Pitch
 - ¾" x 4" Down Rod
 - 78" Lead Wire
 - Includes: (3) GU10 Base, 50 Watt MR16 Halogen Lamps
- Airflow:** 3665 Cubic Feet Per Minute
Electricity Use: 57 Watts (excludes lights)
Airflow Efficiency: 64 Cubic Feet Per Minute Per Watt

SPECIFICATIONS

- Limited Lifetime Warranty
 - Silicon Steel Motor 153mm X 17mm
 - 12° Blade Pitch
 - ¾" x 4" Down Rod
 - 78" Lead Wire
 - Includes: (3) GU10 Base, 50 Watt MR16 Halogen Lamps
- Airflow:** 4682 Cubic Feet Per Minute
Electricity Use: 57 Watts (excludes lights)
Airflow Efficiency: 82 Cubic Feet Per Minute Per Watt



48" Elite

78505
48" Brushed Nickel Finish
Beech Plywood Blades
Includes Light Fixture with Brushed Nickel Spot Lights

52" Castle



72477
52" Brushed Nickel Finish
Reversible Plywood Blades (Weathered Maple/Beech)
Includes Light Fixture with Opal Frosted Glass

SPECIFICATIONS

- Limited Lifetime Warranty
 - Cold Rolled Steel Motor 153mm X 15mm
 - 12° Blade Pitch
 - ¾" x 6" Down Rod
 - 78" Lead Wire
 - Includes: (2) Medium Base, 13 Watt CFL Mini-Twists
- Airflow:** 4819 Cubic Feet Per Minute Per Watt
Electricity Use: 66 Watts (excludes lights)
Airflow Efficiency: 73 Cubic Feet Per Minute Per Watt

Compact Fluorescent Lamps contain mercury.  For more on clean up and safe disposal, visit epa.gov/cfl.

44" Xavier



7226565

44" Brushed Nickel Finish with Copper Accents

*Reversible Blades (Maple/Mahogany)
Includes Light Fixture with Spot Lights*

52" Xavier II



7234265

52" Brushed Nickel Finish with Gun Metal Accents

*Reversible Blades (Graphite/Weathered Maple)
Includes Light Fixture with Spot Lights*

SPECIFICATIONS

- Limited Lifetime Warranty
- Silicon Steel Motor 153mm X 15mm
- 13° Blade Pitch
- 3/4" x 4" Down Rod
- 78" Lead Wire
- Includes: (3) GU10 Base, 50 Watt MR16 Halogen Lamps

7226565 Airflow: 4381 Cubic Feet Per Minute
Electricity Use: 65 Watts (excludes lights)
Airflow Efficiency: 67 Cubic Feet Per Minute Per Watt

7234265 Airflow: 5063 Cubic Feet Per Minute
Electricity Use: 67 Watts (excludes lights)
Airflow Efficiency: 76 Cubic Feet Per Minute Per Watt

52" Panorama



72559

52" Chrome Finish

*Reversible Blades (High Gloss White/Black)
Includes Light Fixture with Opal Frosted Glass Shades*

SPECIFICATIONS

- Limited Lifetime Warranty
- Silicon Steel Motor 153mm X 17mm
- 12° Blade Pitch
- 3/4" x 4" Down Rod
- 54" Lead Wire
- Includes: (4) Medium Base, 14 Watt CFL Mini-Twists

Airflow: 4733 Cubic Feet Per Minute
Electricity Use: 63 Watts (excludes lights)
Airflow Efficiency: 75 Cubic Feet Per Minute Per Watt

Compact Fluorescent Lamps contain mercury. For more on clean up and safe disposal, visit epa.gov/cfl.

TRADITIONAL

ceiling fan collection

Known for their classic and distinctive designs, traditional-styled fans are the most popular. Available in many finishes including antique brass, rustic bronze and brushed nickel, we offer colors and styles to match any décor.



52" Fairview

Collection



78400

52" Brushed Nickel Finish

*Reversible Blades (Weathered Maple/Dark Cherry)
Includes Light Fixture with Frosted Glass Bowl*

SPECIFICATIONS

- Limited Lifetime Warranty
- Cold Rolled Steel Motor 153mm X 12mm
- 11° Blade Pitch
- ¾" x 4" Down Rod
- 24" Lead Wire
- Includes Remote Control
- Includes: (2) Candelabra Base, 60 Watt G16 1/2 Lamps

Airflow: 4370 Cubic Feet Per Minute

Electricity Use: 55 Watts (excludes lights)

Airflow Efficiency: 80 Cubic Feet Per Minute Per Watt



78399

52" Oil Rubbed Bronze Finish

*Reversible Blades (Dark Cherry/Walnut)
Includes Light Fixture with Frosted Glass Bowl*

52" Bethany

7879965
52" Rustic Bronze Finish
 Reversible Blades
 (Mahogany/Rich Walnut)
 Includes Light Fixture with
 Crème Agate Glass Bowl



SPECIFICATIONS

- Limited Lifetime Warranty
 - Cold Rolled Steel Motor 153mm X 15mm
 - 11° Blade Pitch
 - ¾" x 4" Down Rod
 - 78" Lead Wire
 - Includes: (2) Candelabra Base, 60 Watt G16 1/2 Lamps
- Airflow:** 4757 Cubic Feet Per Minute
Electricity Use: 65 Watts (excludes lights)
Airflow Efficiency: 73 Cubic Feet Per Minute Per Watt

52" Sumter Collection



72476
52" Brushed Nickel Finish
 Reversible Blades (Weathered Maple/Beech)
 Includes Light Fixture with White Alabaster Glass Bowl

SPECIFICATIONS

- Limited Lifetime Warranty
 - Cold Rolled Steel Motor 153mm X 15mm
 - 12° Blade Pitch
 - 12" Lead Wire
 - Use (2) Candelabra Base, G16 1/2 Lamps, 60 Watt Maximum (not included)
- Airflow:** 4410 Cubic Feet Per Minute
Electricity Use: 60 Watts (excludes lights)
Airflow Efficiency: 74 Cubic Feet Per Minute Per Watt



72470
52" Classic Bronze Finish
 Reversible Blades
 (Applewood with Shaded Edges/Dark Cherry)
 Includes Light Fixture with Amber Alabaster Glass Bowl

52" Swirl Collection



7856865

52" Rustic Bronze Finish

*Reversible Blades (Mahogany/Rich Walnut)
Includes Light Fixture with
Frosted Swirl Glass Shades*

7807965

52" White Finish

*Reversible Blades
(White/White Washed Pine)
Includes Light Fixture
with Frosted Swirl Glass Shades*



7807765

52" Brushed Pewter Finish

*Reversible Blades (Light Maple/White)
Includes Light Fixture with
Frosted Swirl Glass Shades*



7852165

52" Brushed Nickel Finish

*Reversible Blades (Rosewood/Light Maple)
Includes Light Fixture with
Frosted Swirl Glass Shades*

SPECIFICATIONS

- Limited Lifetime Warranty
- Cold Rolled Steel Motor 153mm X 15mm
- 11° Blade Pitch
- 3/4" x 4" Down Rod
- 78" Lead Wire
- Includes: (4) Candelabra Base, 40 Watt Torpedo Lamps

Airflow: 4831 Cubic Feet Per Minute

Electricity Use: 66 Watts (excludes lights)

Airflow Efficiency: 73 Cubic Feet Per Minute Per Watt

52" Vintage Collection



7804365

52" Polished Brass Finish

*Reversible Blades (Walnut/Oak)
Includes Light Fixture
with Clear Ribbed Glass Shades*



7867865

52" Brushed Nickel Finish

*Reversible Blades (Rosewood/Light Maple)
Includes Light Fixture
with Frosted Ribbed Glass Shades*

SPECIFICATIONS

- Limited Lifetime Warranty
 - Cold Rolled Steel Motor 153mm X 15mm
 - 11° Blade Pitch
 - 3/4" x 4" Down Rod
 - 78" Lead Wire
 - Includes: (3) Candelabra Base, 60 Watt Torpedo Lamps
- Airflow:** 4815 Cubic Feet Per Minute
Electricity Use: 66 Watts (excludes lights)
Airflow Efficiency: 73 Cubic Feet Per Minute Per Watt



7862765

52" White Finish

*Reversible Blades
(White/White Washed Pine)
Includes Light Fixture
with Frosted Ribbed Glass Shades*

52" Vintage II

SPECIFICATIONS

- Limited Lifetime Warranty
 - Cold Rolled Steel Motor 153mm X 12mm
 - 11° Blade Pitch
 - 3/4" x 4" Down Rod
 - 78" Lead Wire
 - Includes: (2) Candelabra Base, 60 Watt G16 1/2 Lamps
- Airflow:** 4435 Cubic Feet Per Minute
Electricity Use: 60 Watts (excludes lights)
Airflow Efficiency: 74 Cubic Feet Per Minute Per Watt



7839165

52" Brushed Nickel Finish

*Reversible Blades (Rosewood/Light Maple)
Includes Light Fixture with Frosted White Alabaster Glass Bowl*

42" Richboro SE

Collection

SPECIFICATIONS

- Limited Lifetime Warranty
 - Silicon Steel Motor 153mm X 10mm
 - 12° Blade Pitch
 - ¾" x 4" Down Rod
 - 78" Lead Wire
 - Includes: (2) Candelabra Base, 60 Watt G16 1/2 Lamps
- Airflow:** 2995 Cubic Feet Per Minute
Electricity Use: 44 Watts (excludes lights)
Airflow Efficiency: 68 Cubic Feet Per Minute Per Watt



7877365

42" Brushed Nickel Finish

*Reversible Blades
 (Rosewood/Light Maple)
 Includes Light Fixture with
 Frosted White Alabaster Glass Bowl*



7826765

42" Rustic Bronze Finish

*Reversible Blades
 (Mahogany/Rich Walnut)
 Includes Light Fixture with
 Frosted White Alabaster Glass Bowl*

42" Newtown

SPECIFICATIONS

- Limited Lifetime Warranty
 - Cold Rolled Steel Motor 153mm X 10mm
 - 12° Blade Pitch
 - ¾" x 4" Down Rod
 - 78" Lead Wire
 - Includes: (3) Candelabra Base, 60 Watt Torpedo Lamps
- Airflow:** 3446 Cubic Feet Per Minute
Electricity Use: 55 Watts (excludes lights)
Airflow Efficiency: 63 Cubic Feet Per Minute Per Watt



7843565

42" Brushed Nickel Finish

*Reversible Blades (Light Maple/Bird's Eye Maple)
 Includes Light Fixture with Water Glass Shades*

42" Contempra Trio Collection



78615

42" Brushed Nickel Finish

*Reversible Blades (Rosewood/Bird's Eye Maple)
Includes Light Fixture with Frosted Glass Shades*



78377

42" Oil Rubbed Bronze Finish

*Reversible Blades (Dark Cherry/Walnut)
Includes Light Fixture with Frosted Glass Shades*



78509

42" Satin Brass Finish

*Reversible Blades (Walnut/Maple)
Includes Light Fixture
with Frosted Glass Shades*

78510
42" Antique Brass Finish
*Reversible Blades (Oak/Walnut)
Includes Light Fixture
with Frosted Glass Shades*



78508

42" White Finish

*Reversible Blades
(White/White Washed Pine)
Includes Light Fixture
with Frosted Glass Shades*

SPECIFICATIONS

- Limited Lifetime Warranty
- Cold Rolled Steel Motor: 153mm x 10mm
- 12° Blade Pitch
- 12" Lead Wire
- Use (3) Candelabra Base Lamps, 60 Watt Maximum (not included).

Airflow: 4410 Cubic Feet Per Minute

Electricity Use: 54 Watts (excludes lights)

Airflow Efficiency: 82 Cubic Feet Per Minute Per Watt



52" Contempra IV

Collection

SPECIFICATIONS

- Limited Lifetime Warranty
- Cold Rolled Steel Motor 153mm X 15mm
- 11° Blade Pitch
- 12" Lead Wire
- Use (4) Candelabra Base,

60 Watt Maximum (not included)

Airflow: 4410 Cubic Feet Per Minute

Electricity Use: 63 Watts (excludes lights)

Airflow Efficiency: 70 Cubic Feet Per Minute Per Watt



78660

52" Oil Rubbed Bronze Finish
Reversible Blades (Dark Cherry/Walnut)
Includes Light Fixture with
Frosted Ribbed Glass Shades



78716

52" Polished Brass Finish
Reversible Blades (Walnut/Oak)
Includes Light Fixture with
Clear Ribbed Glass Shades

78714

52" Antique Brass Finish
Reversible Blades (Oak/Walnut)
Includes Light Fixture with
Frosted Ribbed Glass Shades



52" Contempra IV

Collection



SPECIFICATIONS

- Limited Lifetime Warranty
 - Cold Rolled Steel Motor 153mm X 15mm
 - 11° Blade Pitch
 - 12" Lead Wire
 - Use (4) Candelabra Base, 60 Watt Maximum (not included)
- Airflow:** 4410 Cubic Feet Per Minute
Electricity Use: 63 Watts (excludes lights)
Airflow Efficiency: 70 Cubic Feet Per Minute Per Watt

78715

52" White Finish

*Reversible Blades (White/White Washed Pine)
Includes Light Fixture with Frosted Ribbed Glass Shades*



78616

52" Brushed Nickel Finish

*Reversible Blades (Rosewood/Bird's Eye Maple)
Includes Light Fixture with Frosted Ribbed Glass Shades*

52" Contempra V



SPECIFICATIONS

- Limited Lifetime Warranty
 - Cold Rolled Steel Motor 153mm X 15mm
 - 11° Blade Pitch
 - 12" Lead Wire
 - Use (4) Candelabra Base Lamps, 40 Watt Maximum (not included)
- Airflow:** 4410 Cubic Feet Per Minute
Electricity Use: 70 Watts (excludes lights)
Airflow Efficiency: 63 Cubic Feet Per Minute Per Watt

78004

52" Brushed Nickel Finish

*Reversible Blades
(Rosewood/Bird's Eye Maple)
Includes Light Fixture with
Frosted Alabaster Glass Shades*



78005
30" Brushed Nickel Finish
 Reversible Blades
 (Rosewood/Light Maple)
 Includes Light Fixture
 with Opal Mushroom Glass

30" Petite Collection



78603
30" Antique Brass Finish
 Reversible Blades (Walnut/Oak)
 Includes Light Fixture with
 Opal Mushroom Glass



78108
30" White Finish
 Reversible Blades
 (White/White Washed Pine)
 Includes Light Fixture with Opal Mushroom Glass

SPECIFICATIONS

- Limited Lifetime Warranty
 - Cold Rolled Steel Motor 153mm X 9mm
 - 18° Blade Pitch
 - 12" Lead Wire
 - Use (1) Candelabra Base, 60 Watt Maximum (not included)
- Airflow:** 3925 Cubic Feet Per Minute
Electricity Use: 45 Watts (excludes lights)
Airflow Efficiency: 87 Cubic Feet Per Minute Per Watt

52" Casanova

78053
52" White Finish
 Reversible Blades
 (White/White Washed Pine)

SPECIFICATIONS

- Limited Lifetime Warranty
 - Cold Rolled Steel Motor 153mm X 15mm
 - 11° Blade Pitch
 - 12" Lead Wire
- Airflow:** 5098 Cubic Feet Per Minute
Electricity Use: 60 Watts (excludes lights)
Airflow Efficiency: 85 Cubic Feet Per Minute Per Watt



42" Casanova Supreme Collection



78123

42" Antique Brass Finish

*Reversible Blades (Oak/Walnut)
Includes Light Fixture with
Opal Schoolhouse Glass*

SPECIFICATIONS

- Limited Lifetime Warranty
 - Cold Rolled Steel Motor 153mm X 10mm
 - 12° Blade Pitch
 - 12" Lead Wire
 - Use (1) Candelabra Base Lamp, 60 Watt Maximum (not included)
- Airflow:** 4410 Cubic Feet Per Minute
Electricity Use: 56 Watts (excludes lights)
Airflow Efficiency: 79 Cubic Feet Per Minute Per Watt



78126

42" White Finish

*Reversible Blades
(White/White Washed Pine)
Includes Light Fixture with
Opal Schoolhouse Glass*



78125

42" Polished Brass Finish

*Reversible Blades (Walnut/Oak)
Includes Light Fixture with
Opal Schoolhouse Glass*

42" Princess Ambiance

SPECIFICATIONS

- Limited Lifetime Warranty
 - Cold Rolled Steel Motor 153mm X 10mm
 - 12° Blade Pitch
 - ¾" x 4" Down Rod
 - 78" Lead Wire
 - Includes: (1) Candelabra Base, 60 Watt G16 1/2 Lamp
- Airflow:** 3540 Cubic Feet Per Minute
Electricity Use: 53 Watts (excludes lights)
Airflow Efficiency: 67 Cubic Feet Per Minute Per Watt



7813365

42" White Finish

*Reversible Blades
(White/White Washed Pine)
Includes Light Fixture
with Opal Mushroom Glass*



Westinghouse

INNOVATION YOU CAN BE SURE OF

INDOOR/OUTDOOR ceiling fan collection...

Bring indoor comfort outdoors with Westinghouse ceiling fans designed specially for patios, verandahs and gazebos. Our indoor/outdoor ceiling fans are suitable for wet locations.

new!



52" Brentford

78000

52" Aged Walnut Finish

*Reversible ABS Blades
(Dark Cherry Shaded Edges/Walnut)*

*Includes Light Fixture
with Clear Seeded Glass*

SPECIFICATIONS

- Limited Lifetime Warranty
- Silicon Steel Motor 153mm X 17mm
- 13° Blade Pitch
- 3/4" x 4" Down Rod
- 54" Lead Wire
- Includes: (3) Candelabra Base,
40 Watt Torpedo Lamps

Airflow: 5062 Cubic Feet Per Minute

Electricity Use: 55 Watts (excludes lights)

Airflow Efficiency: 92 Cubic Feet Per Minute Per Watt



52" Lafayette

Collection



SPECIFICATIONS

- Limited Lifetime Warranty
 - Silicon Steel Motor 153mm X 15mm
 - 12° Blade Pitch
 - 3/4" x 6" Down Rod
 - 54" Lead Wire
 - Includes: (1) Medium Base, 13 Watt CFL Mini-Twist
- Airflow:** 5083 Cubic Feet Per Minute
Electricity Use: 65 Watts (excludes lights)
Airflow Efficiency: 78 Cubic Feet Per Minute Per Watt



7877965
52" Antique Pewter Finish
 Black ABS Resin Blades

Includes Light Fixture with White Alabaster Glass



7877865
52" Weathered Iron Finish
 Light Oak ABS Resin Blades

Includes Light Fixture with Yellow Alabaster Glass

48" Oasis



SPECIFICATIONS

- Limited Lifetime Warranty
 - Silicon Steel Motor 153mm X 15mm
 - 13° Blade Pitch
 - 3/4" x 6" Down Rod
 - 54" Lead Wire
 - Includes: (1) Candelabra Base, G16 1/2 Lamp, 60 Watt Maximum
- Airflow:** 4305 Cubic Feet Per Minute
Electricity Use: 57 Watts (excludes lights)
Airflow Efficiency: 76 Cubic Feet Per Minute Per Watt

7861965

48" Oil Rubbed Bronze Finish
 Mahogany Leaf
 ABS Resin Blades

*Includes Light Fixture with
 Yellow Alabaster Glass*

Compact Fluorescent Lamps contain mercury. For more on clean up and safe disposal, visit epa.gov/cfl.

44" Bayside

SPECIFICATIONS

- Limited Lifetime Warranty
- Silicon Steel Motor 153mm X 12mm
- 12° Blade Pitch
- ¾" x 4" Down Rod
- 54" Lead Wire

Airflow: 3673 Cubic Feet Per Minute

Electricity Use: 48 Watts (excludes lights)

Airflow Efficiency: 77 Cubic Feet Per Minute Per Watt



72345

44" Oil Rubbed Bronze Finish

Dark Cherry ABS Resin Blades

52" Willow Breeze Collection

SPECIFICATIONS

- Limited Lifetime Warranty
- Silicon Steel Motor 153mm X 15mm
- 12° Blade Pitch
- ¾" x 4" Down Rod
- 54" Lead Wire

Airflow: 5290 Cubic Feet Per Minute

Electricity Use: 58 Watts (excludes lights)

Airflow Efficiency: 91 Cubic Feet Per Minute Per Watt



72478

52" Oil Rubbed Bronze Finish

Dark Cherry ABS Resin Blades



72280

52" White Finish

White ABS Resin Blades



INDUSTRIAL & contractor ceiling fan collection

Commercial environments need durable, reliable ceiling fans. Our industrial and contractor ceiling fans have the quality you want and expect from an international brand.



Caution: Industrial Ceiling Fans must be installed with blades at least 10 feet from the floor.

56" Industrial Collection

78614

56" Brushed Nickel Finish

*Brushed Nickel Finish Steel Blades
Ball Hanger Installation System*




SPECIFICATIONS

- 15 Year Limited Warranty
 - Cold Rolled Steel Motor 153mm X 17mm
 - 9° Blade Pitch
 - ½" x 12" Down Rod
 - Lead Wire: 78" - 78127, 78614
24" - 78409
 - Includes Wall Control
- Airflow:** 6254 Cubic Feet Per Minute
Electricity Use: 60 Watts (excludes lights)
Airflow Efficiency: 104 Cubic Feet Per Minute Per Watt

78127

56" White Finish

*White Steel Blades
Ball Hanger Installation System*



78409

56" White Finish

*White Steel Blades
J-Hook Installation System*



**J-Hook
Installation System**



56" Industrial Collection

78003
56" Brushed Nickel Finish
Black Steel Blades
Ball Hanger Installation System



SPECIFICATIONS

- 15 Year Limited Warranty
 - Cold Rolled Steel Motor 153mm X 17mm
 - 8° Blade Pitch
 - ½" x 12" Down Rod
 - 78" Lead Wire
 - Includes Wall Control
- Airflow:** 6254 Cubic Feet Per Minute
Electricity Use: 60 Watts (excludes lights)
Airflow Efficiency: 104 Cubic Feet Per Minute Per Watt

52" Contractor's Choice



78024
52" White Finish
White Blades

SPECIFICATIONS


- Limited Lifetime Warranty
 - Silicon Steel Motor 153mm X 15mm
 - 12° Blade Pitch
 - ¾" x 4" Down Rod
 - 78" Lead Wire
- Airflow:** 4726 Cubic Feet Per Minute
Electricity Use: 65 Watts (excludes lights)
Airflow Efficiency: 73 Cubic Feet Per Minute Per Watt

CEILING FAN SPECIFICATIONS

Family Name	Page #	Size	# of Blades	Blade Material	Capacitor	Extra Switch Housing Cap	Fan Mounting	Airflow CFM (High)	RPM (High)	Electricity Use-Watts (High)	Efficiency CFM/W (High)	Amp	Remote Control	Slope Angle
Alloy	97	42"	3	MDF	Dual	No	Down Rod Only	4083	215	51	80	0.42	Adaptable	15°
Arcadia	98	46"	3	Plywood	Triple	No	Combo	4300	242	52	82	0.43	Included	20°
Bayside	116	44"	5	ABS Resin	Triple	No	Combo	3673	220	48	77	0.40	Adaptable	11°
Bendan	93	52"	5	Plywood	Dual	No	Down Rod Only	4739	175	60	79	0.51	Included	N/A
Bethany	105	52"	5	MDF	Triple	No	Combo	4757	170	65	73	0.52	Adaptable	18°
Brentford	114	52"	5	ABS Resin	Triple	No	Down Rod Only	5062	168	55	92	0.46	Adaptable	20°
Casanova	112	52"	5	MDF	Triple	No	Hugger	5098	180	60	85	0.50	Not Adaptable	N/A
Casanova Supreme	113	42"	4	MDF	Dual	Yes	Hugger	4410	220	56	79	0.45	Not Adaptable	N/A
Castle	101	52"	5	Plywood	Triple	No	Combo	4819	171	66	73	0.55	Adaptable	18°
Comet	100	52"	5	Plywood	Triple	No	Combo	5199	165	61	85	0.50	Adaptable	18°
Contempra IV	110	52"	5	MDF	Triple	No	Hugger	4410	165	63	70	0.52	Not Adaptable	N/A
Contempra V	111	52"	5	MDF	Triple	No	Hugger	4410	165	70	63	0.52	Not Adaptable	N/A
Contempra Trio	109	42"	5	MDF	Dual	Yes	Hugger	4410	220	54	82	0.45	Not Adaptable	N/A
Contractor's Choice	119	52"	5	MDF	Triple	No	Combo	4726	175	65	73	0.52	Adaptable	11°
Cumulus	97	48"	3	MDF	Triple	No	Down Rod Only	4804	210	52	93	0.43	Included	N/A
Delancey	93	52"	3	ABS Resin	N/A	No	Down Rod Only	5722	194	32	178	0.46	Included	20°
Elite	101	48"	3	Plywood	Triple	No	Combo	4682	230	57	82	0.49	Adaptable	18°
Fairview	104	52"	5	MDF	Dual	No	Combo	4370	170	55	80	0.47	Included	N/A
Harmony	99	48"	2	Plywood	Triple	No	Down Rod Only	4881	230	53	92	0.46	Adaptable	20°
Industrial	118	56"	3	Steel	Single	No	Down Rod Only	6254	240	60	104	0.50	Wall Control	24° N/A for 78409
Industrial 78003	119	56"	3	Steel	Single	No	Down Rod Only	6254	240	60	104	0.50	Wall Control	24°
Lafayette	115	52"	5	ABS Resin	Triple	Yes	Combo	5083	170	65	78	0.47	Adaptable	11°
Lavada	98	48"	3	Plywood	Triple	No	Down Rod Only	4757	204	52	91	0.44	Adaptable	20°
Newtown	108	42"	5	MDF	Dual	No	Combo	3446	220	55	63	0.45	Adaptable	18°
Oasis	115	48"	5	ABS Resin	Triple	Yes	Combo	4305	215	57	76	0.47	Adaptable	11°
Origami	94	24"	6	MDF	Dual	No	Down Rod Only	2039	309	31	66	0.25	Adaptable	18°
Panorama	102	52"	5	MDF	Triple	Yes	Combo	4733	160	63	75	0.53	Adaptable	15°
Petite	112	30"	6	MDF	Dual	No	Hugger	3925	270	45	87	0.36	Not Adaptable	N/A
Princess Ambiance	113	42"	4	MDF	Triple	No	Combo	3540	220	53	67	0.44	Adaptable	18°
Quince	94	24"	6	MDF	Dual	No	Down Rod Only	2039	320	31	67	0.25	Adaptable	18°
Richboro SE	108	42"	5	MDF	Dual	No	Combo	2995	215	44	68	0.45	Adaptable	15°
Roundabout	95	30"	5	MDF	Dual	No	Down Rod Only	2483	265	39	63	0.34	Adaptable	18°
Solana	99	48"	2	Plywood	Triple	No	Down Rod Only	3313	220	49	68	0.42	Included	30°
Sparta	99	52"	2	Plywood	Triple	No	Down Rod Only	5017	205	54	93	0.45	Included	20°
Sumter	105	52"	5	MDF	Triple	No	Hugger	4410	170	60	74	0.51	Not Adaptable	N/A
Swirl	106	52"	5	MDF	Triple	No	Combo	4831	170	66	73	0.55	Adaptable	18°
Techno	93	52"	3	ABS Resin	Triple	No	Down Rod Only	4264	234	52	82	0.47	Included	20°
Turbo Swirl	96	30"	6	MDF	Dual	No	Combo	2541	260	52	49	0.36	Adaptable	18°
Turbo Swirl CFL	96	30"	6	MDF	Dual	No	Combo	3519	246	50	70	0.42	Adaptable	18°
Vector Elite	101	42"	3	Plywood	Triple	No	Combo	3665	220	57	64	0.47	Adaptable	19°
Vintage	107	52"	5	MDF	Triple	No	Combo	4815	170	66	73	0.55	Adaptable	18°
Vintage II	107	52"	5	MDF	Triple	Yes	Combo	4435	170	60	74	0.50	Adaptable	18°
Wengue	95	30"	3	MDF	Dual	No	Down Rod Only	2543	280	40	64	0.33	Adaptable	18°
Willow Breeze	116	52"	5	ABS Resin	Triple	No	Combo	5290	185	58	91	0.48	Adaptable	12°
Xavier	102	44"	5	MDF	Triple	Yes	Combo	4381	210	65	67	0.54	Adaptable	17°
Xavier II	102	52"	5	MDF	Triple	Yes	Combo	5063	170	67	76	0.56	Adaptable	17°



Visit www.westinghouselighting.com for FTC energy guide information.



- A - Top of Canopy to Bottom of Blade
- B - Top of Canopy to Bottom of Switch Housing
- C - Top of Canopy to Bottom of Canopy
- D - Width of Motor Housing
- E - Width of Canopy
- F - Top of Canopy to Bottom of Glass

CEILING FAN SPECIFICATIONS - DIMENSIONS

Family Name	Size of Down Rod Included	A	B	C	D	E	F
Alloy	3/4" x 4"	6.38"	11"	2.5"	6.75"	5.13"	11.75"
Arcadia	3/4" x 4"	9.38"	11"	2"	9.75"	5.88"	14"
Bayside	3/4" x 4"	11"	11.38"	2.38"	8.88"	5.13"	N/A
Bendan	3/4" x 4"	10"	N/A	2.5"	10.25"	5.13"	13.75"
Bethany	3/4" x 4"	12.63"	12.5"	2.38"	12.13"	5.13"	17.5"
Brentford	3/4" x 4"	9.96"	11.65"	2.06"	12.36"	5.83"	18.78"
Casanova	N/A	8"	8.5"	N/A	11"	N/A	N/A
Casanova Supreme	N/A	7.25"	8.5"	N/A	8.75"	N/A	12.5"
Castle	3/4" x 6"	11.43"	12.63"	2.4"	10.49"	5.13"	15.98"
Comet	3/4" x 4"	11.88"	14.25"	2.25"	11.5"	5.13"	14.25"
Contempra IV	N/A	7.13"	8.13"	N/A	11.5"	N/A	13"
Contempra V	N/A	7.83"	8.13"	N/A	11.5"	N/A	12.9"
Contempra Trio	N/A	5.88"	7.5"	N/A	10.38"	N/A	13.38"
Contractor's Choice	3/4" x 4"	10.25"	11.25"	2.25"	9"	5.25"	N/A
Cumulus	N/A	15.93"	19.3"	2.75"	7.28"	5.2"	21.3"
Delancey	3/4" x 4"	12.24"	12.52"	2.06"	7.87"	6.14"	15.47"
Elite	3/4" x 4"	9.63"	12.63"	2.13"	9"	5.25"	16.63"
Fairview	3/4" x 4"	12.25"	13"	2.38"	11"	5.13"	18.88"
Harmony	3/4" x 6"	10.63"	12.75"	2"	7.5"	6"	17.13"
Industrial	1/2" x 12"	17.25"	N/A	2.38"	7.75"	5.13"	N/A
Industrial 78003	1/2" x 12"	17.25"	N/A	2.38"	7.75"	5.13"	N/A
Lafayette	3/4" x 6"	15.5"	16.13"	2.38"	12.25"	5.13"	24"
Lavada	3/4" x 4"	8.07"	11.42"	2.07"	7.87"	6.14"	12.6"
Newtown	3/4" x 4"	11.38"	12.63"	2.38"	10"	5.13"	17.75"
Oasis	3/4" x 4"	13.63"	13.38"	2.38"	9"	5.13"	18.75"
Origami	3/4" x 4"	7.88"	10"	2.5"	6.75"	5.13"	14.75"
Panorama	3/4" x 4"	12.62"	9"	2.5"	10.75"	5.12"	15.87"
Petite	N/A	6.75"	8"	N/A	9"	N/A	12"
Princess Ambiance	3/4" x 4"	12.25"	12.5"	2.13"	6.63"	5.25"	16.88"
Quince	3/4" x 4"	9"	10.38"	2.5"	6.75"	5.13"	12.13"
Richboro SE	3/4" x 4"	12.25"	18.13"	2.25"	8.63"	5.13"	17"
Roundabout	3/4" x 4"	11.42"	13.75"	2.36"	7.68"	5.12"	15.92"
Solana	3/4" x 4"	10.75"	13"	2"	7.63"	6.25"	17.38"
Sparta	3/4" x 4"	10.7"	11.6"	2.1"	9.1"	5.86"	13"
Sumter	N/A	6"	7.87"	N/A	11.42"	N/A	14.2"
Swirl	3/4" x 4"	13.5"	12"	2.25"	12"	5.25"	18"
Techno	3/4" x 4"	9.13"	11.02"	2.06"	8.39"	6.14"	12.4"
Turbo Swirl	3/4" x 4"	10"	11.5"	2.25"	7"	5"	14.5"
Turbo Swirl CFL	3/4" x 4"	10"	11.5"	2.25"	7"	5"	16.5"
Vector Elite	3/4" x 4"	7"	11.25"	2.13"	10.38"	5.13"	15.5"
Vintage	3/4" x 4"	11"	13"	2"	11"	5"	18"
Vintage II	3/4" x 4"	11.38"	13.25"	2.38"	11.13"	5.13"	19.25"
Wengue	3/4" x 4"	9"	10.38"	2.5"	6.75"	5.13"	12.13"
Willow Breeze	3/4" x 4"	11.1"	13.3"	2.4"	11.6"	5.1"	N/A
Xavier	3/4" x 4"	16"	17.5"	2"	10"	5"	22.5"
Xavier II	3/4" x 4"	16"	17.5"	2"	10"	5"	22.5"

If a Combo Style Fan with a 4" Down Rod is Installed without the Down Rod, Subtract 3" from the Dimensions Listed (A, B, F).
 If a Combo Style Fan with a 6" Down Rod is Installed without the Down Rod, Subtract 5" from the Dimensions Listed (A, B, F).



CEILING FAN

accessories

Compliment your Westinghouse ceiling fans with decorative pull chains and energy-saving light kits, while enjoying the convenience of our fan remote controls.



Ceiling Fan Light Kits

Schoolhouse Light Kits
Height: 6.75"
Diameter: 8.25"



77813



77838



77832



77811



Light kit includes one medium base, 13 watt maximum ENERGY STAR® CFL Mini-Twist.

Item No.	Description	Finish	Glass Description
77811	Schoolhouse Light Kit, Damp Location	Polished Brass	White Glass
77813	Schoolhouse Light Kit, Damp Location	Oil Rubbed Bronze	White Glass
77832	Schoolhouse Light Kit, Damp Location	Antique Brass	White Glass
77838	Schoolhouse Light Kit, Damp Location	White	White Glass

3 Light Cluster Light Kits
Height: 7"
Width: 12.75"



77812



77823



77814



Light Kit includes three medium base, 9 watt maximum ENERGY STAR® CFL Mini-Twists.



77815



77826

Item No.	Description	Finish	Glass Description
77812	3 Light Cluster Light Kit	Polished Brass	Frosted Ribbed Glass Shades
77814	3 Light Cluster Light Kit	White	Frosted Ribbed Glass Shades
77815	3 Light Cluster Light Kit	Antique Brass	Frosted Ribbed Glass Shades
77823	3 Light Cluster Light Kit	Brushed Nickel	Frosted Ribbed Glass Shades
77826	3 Light Cluster Light Kit	Oil Rubbed Bronze	Frosted Ribbed Glass Shades

Designed to work with standard 42" to 52" ceiling fans with a center hole in the housing cap.



Compact Fluorescent Lamps contain mercury. (Hg) For more on clean up and safe disposal, visit epa.gov/cfl.



Extension Down Rods

For optimum performance, ceiling fan blades should be at least 7' from the floor but no higher than 8-9' in order to best cool a room.

For ceilings 9' and higher, an extension down rod is required to bring the ceiling fan down to the proper height above the floor.



1/2" EXTENSION DOWN RODS					
Finish	12"	18"	24"	36"	48"
Antique Brass	77241	N/A	77244	N/A	N/A
Brushed Nickel	77491	N/A	77492	N/A	N/A
Polished Brass	77242	N/A	77245	N/A	N/A
White	77240	N/A	77243	77246	N/A

1/2" is the nominal dimension of these downrods.

3/4" EXTENSION DOWN RODS				
Finish	12"	18"	24"	36"
Antique Brass	77249	N/A	77252	77255
Brushed Nickel	77526	N/A	77527	77528
Oil Rubbed Bronze	65680	N/A	65682	N/A
Polished Brass	77934	N/A	77935	N/A
Rustic Bronze	65659	N/A	65661	N/A
White	77251	77265	77254	77257

3/4" is the nominal dimension of these downrods.

The chart below is provided for convenient selection of the correct extension down rod.

Ceiling Height 9'	Ceiling Height 10'	Ceiling Height 11'	Ceiling Height 12'	Ceiling Height 13'
Extension Down Rod 12"	Extension Down Rod 18"	Extension Down Rod 24"	Extension Down Rod 36"	Extension Down Rod 48"

Ceiling Fan Controls



77872 Single Slide Ceiling Fan Wall Control

- Turn any 3 speed fan into a 4 speed fan
- High/Medium-High/Medium/Low fan speeds
- Easy 2 wire installation in standard junction box
- Matching wall plate included

Max. Fan Amp 1.25



77870 Ceiling Fan and Light Remote Control

- High/Medium/Low fan speeds and Off button
- Full range light dimmer
- Operates up to a distance of 40 feet
- Universal receiver fits most ceiling fans
- Installs quickly, even in pre-mounted fans
- Wall Bracket included
- (1) 9 Volt battery included

Max. Fan Amp 1.25
Max. Light 300 Watt



77873 Dual Slide Ceiling Fan/Light Wall Control

- Turn any 3 speed fan into a 4 speed fan
- High/Medium-High/Medium/Low fan speeds
- Full range sliding light dimmer
- Easy 3 wire installation in standard junction box
- Replaces toggle switch
- Matching wall plate included

Max. Fan Amp 1.25
Max. Light 300 Watt



77874 Thermostat Ceiling Fan/Light Remote Control

- Automatic On/Off and Speed Control based on room temperature
- ½ - 24 hour programmable fan/light shut off timers
- 3-Minute Auto Light Shut Off
- High/Medium/Low fan speeds and Off button
- Full range light dimmer
- Operates up to a distance of 40 feet
- Universal receiver fits most ceiling fans
- Installs quickly, even in pre-mounted fans
- (4) AAA batteries required (not included)

Max. Fan Amp 1.25
Max. Light 300 Watt



77875 Ceiling Fan and Light Wall Control

- High/Medium/Low fan speeds and Off button
- Full range light dimmer
- Wireless communication between transmitter and receiver
- Operates up to a distance of 40 feet
- Easy 2 wire installation in standard junction box
- Universal receiver fits most ceiling fans
- Matching wall plate included

Max. Fan Amp 1.25
Max. Light 300 Watt



77840 Ceiling Fan and Light Remote Control

- Turn any 3 speed fan into a 4 speed fan
- High/Medium/Medium-Low/Low fan speeds and Off button
- Full range light dimmer
- Operates up to a distance of 40 feet
- Universal receiver fits most ceiling fans
- Installs quickly, even in pre-mounted fans
- Wall Bracket included
- (1) 23A 12 Volt battery included

Max. Fan Amp 1.25
Max. Light 300 Watt

 All fan controls are CUL listed.

Cathedral Ceiling Fan Canopy Kits




Cathedral Ceiling Fan Canopy Kits Include:

- Decorative Canopy
- Retaining Ball
- Universal Mounting Plate
- Mounting Bracket
- Decorative Hole Cover Ring
- Mounting Hardware
- 1/2" Down Rod Sleeve Adapter
- Complete Installation Instructions

The **only** cathedral ceiling fan canopy kit that is remote control adaptable up to a 45° angle. No visible screws. Decorative hole cover ring included for a clean finished look.

This unique patent-pending product is the only cathedral ceiling fan canopy kit that is remote control adaptable. It is easy to install a remote control receiver even up to a 45 degree angle.

Attractive one piece canopy design is available in finishes to coordinate and complement most ceiling fans.



Patent Pending

70029 - White Finish
 70030 - Antique Brass Finish
 70031 - Brushed Nickel Finish
 70032 - Oil Rubbed Bronze Finish
Cathedral Ceiling Fan Canopy Kit

*Can be mounted onto a cathedral ceiling having up to a 45° angle
 For Use With 1/2" or 3/4" I.D. Down Rods
 85 lb. Load Rating*



70032



70029



70030



70031

Pull Chains



77630
Red
Spiral Glass
Brushed
Nickel Finish



77122
Yellow
Spiral Glass
Oil Rubbed
Bronze Finish



77640
Cobalt
Twist Glass
Brushed
Nickel Finish



77635
Filigree Leaf
Glass
Polished
Brass Finish



77628
Burgundy and
Orange Beads
Polished
Brass Finish



77294
Burgundy and
Orange Beads
Chrome Finish



77642
Orange and
Green
Daisy Beads
Polished
Brass Finish



77123
Frosted White
Alabaster Glass
Brushed
Nickel Finish



77125
Amber
Alabaster Glass
Oil Rubbed
Bronze Finish



77620
White Swirl and
Multi-Color Dotted
Glass Orb
Brushed
Nickel Finish



77118
Clear and
Amber Swirls
Glass Orb
Oil Rubbed
Bronze Finish



77621
Clear and
Blue Swirl
Glass Orb
Brushed
Nickel Finish

All pull chains include a 12" beaded chain unless otherwise noted.

77029
Light Bulb
Brushed
Nickel Finish



77030
Light Bulb
Oil Rubbed
Bronze Finish



77220
Light Bulb
Antique
Brass Finish



77036
Fan
Brushed
Nickel Finish



77083
Fan
Oil Rubbed
Bronze Finish



77225
Fan
White
Chrome Finish



77224
Fan
Antique
Brass Finish



77087
Natural Finish
Wooden Handle
Polished
Brass Finish

77291
Walnut
Wooden Cone
Antique
Brass Finish

77009
White
Wooden Cone
Polished
Brass Finish

77292
White
Wooden Cone
Chrome
Finish

77019
Natural Finish
Wooden Cone
Polished
Brass Finish

77008
Walnut
Wooden Cone
Polished
Brass Finish



77014
White
Wooden Knob
Polished
Brass Finish

77013
Walnut
Wooden Knob
Polished
Brass Finish

70661 - 36" Chain
77069 - 12" Chain
Walnut
Wooden Ball
Polished
Brass Finish

77290
Walnut
Wooden Ball
36" Antique
Brass Finish

77072
White
Wooden Ball
Polished
Brass Finish

77007
Sculptured
Walnut
Wooden Ball
Polished
Brass BFinish

All pull chains include a 12" beaded chain unless otherwise noted.

CARDER PRODUCT SOLD IN INNER PACK ONLY

www.westinghouselighting.com

77215
Trophy
Brushed
Nickel Finish



77108
Trophy
Antique
Brass Finish



77214
Trophy
Oil Rubbed
Bronze Finish



77103
Pendant
Brushed
Nickel Finish



77104
Beaded Ball
Brushed
Nickel Finish



77096
Beaded Ball
Oil Rubbed
Bronze Finish



77217
Ball
Brushed
Nickel Finish



77218
Ball
Old Chicago
Finish



77004
Ball
Solid Brass
Finish

77005
Teardrop
Polished
Brass Finish



77121
Chrome Finish
and Ceramic
Black Accent



77095
Polished
Brass Finish
and Ceramic
White Accent



77097
Polished
Brass Finish
and Ceramic
Blue Accent



All pull chains include a 12" beaded chain unless otherwise noted.

77645
Shell
Antique Brass Finish
Converts to a finial



77644
Anchor
Antique Brass Finish



77626
Four Leaf Clover
Antique Bronze Finish



77638
Frog
Brushed Nickel Finish



77006
Acrylic Cylinder
Polished Brass Finish



77088
Acrylic Teardrop
Polished Brass Finish



77084
Acrylic Sphere
Polished Brass Finish



77093
Acrylic Diamond
Polished Brass Finish



77289
Acrylic Diamond
Chrome Finish



77134
Acrylic Dolphin
Polished Brass Finish



77010
Gold Tassel
Polished Brass Finish



77011
White Tassel
Polished Brass Finish



77127
Baseball
Polished Brass Finish



77293
Baseball
Chrome Finish


All pull chains include a 12" beaded chain unless otherwise noted.

CARDER PRODUCT SOLD IN INNER PACK ONLY

www.westinghouselighting.com



77400 - 42" Polished Brass Finish
 77401 - 42" White Finish
 77402 - 42" Antique Brass Finish
 77405 - 52" Polished Brass Finish
 77406 - 52" White Finish
 77407 - 52" Antique Brass Finish
 Replacement Fan Blade Arms
 5 Piece Set
 Installation Hardware Included



FAN BLADE HOLE DIMENSIONS		
Dimension	52" Parts	42" Parts
A	31 ⁵ / ₁₆ "	3 ¹ / ₂ "
B	2 ³ / ₄ "	2 ⁵ / ₈ "
C	2 ¹ / ₁₆ "	1 ¹ / ₁₆ "



77414 - 52" White
 Outdoor ABS Fan Blades
 5 Blade Set



77411 - 42" White/Bleached Oak
 77416 - 52" White/Bleached Oak
 Reversible MDF Fan Blades
 5 Blade Set



77410 - 42" Oak/Walnut
 77415 - 52" Oak/Walnut
 Reversible MDF Fan Blades
 5 Blade Set



77060 - Antique Brass Finish
 77061 - Polished Brass Finish
 77268 - White Finish
 Canopy Kit
 1/2" I.D. Ball Included
 Can be mounted onto a cathedral ceiling having up to a 25° angle
 100 lb. Load Rating



77079 - White Finish
 77074 - Antique Brass Finish
 77076 - Polished Brass Finish
 Canopy Kit
 3/4" I.D. Ball Included
 Can be mounted onto a cathedral ceiling having up to a 25° angle
 100 lb. Load Rating



77105
 All Purpose Electrostatic Duster

- Telescopic handle extends up to 72"
- Flexible head adjusts to any angle
- Perfect for cleaning fan blades, fixtures or any other hard-to-reach household items



7709908
 Duster Display
 Contains 12 Dusters
 (Item# 77105)



77044 - Solid Brass Six Beaded Chain Connectors



77046 - White Six Beaded Chain Connectors



77045 - Chrome Six Beaded Chain Connectors



77066 - Antique Brass Six Beaded Chain Connectors




***16572 - Brass Beaded Chain Connector**

Beaded Chain with Connector

.011 Gauge 1/8" Diameter Ball 75 Balls per Foot

Item No.	Length	Finish
70168	5 Ft.	Brass
77012	1 Ft.	Solid Brass
77050	3 Ft.	Solid Brass
77043	12 Ft.	Solid Brass
77064	3 Ft.	Antique Brass
77109	12 Ft.	Antique Brass
77051	3 Ft.	White Plastic
77054	3 Ft.	Oil Rubbed Bronze
77049	3 Ft.	Stainless Steel
77238	3 Ft.	Brushed Nickel
77063	3 Ft.	Chrome
77107	12 Ft.	Chrome




70168




77012

77049




77050

77238




77043

77063



77051

77054



77107



77064

77109



***16576 - Brass Finish End Bell**
For Beaded Chain or Pull Cord



***22370 77077 Porcelain Fixture Socket**
10" Wire Leads
Medium Base, 1/8-IP Hickey
18 Gauge, 105° Leads
660 Watts Max., 250 Volts
Height - 2"



Beaded Chain

.011 Gauge 1/8" Diameter Ball 75 Balls per Foot

Item No.	Length	Finish
*16565	Sold by Foot or 250' Spool	Nickel
*16564	Sold by Foot or 250' Spool	Brass



77047 - Polished Brass 77048 - Antique Brass 10 Piece Motor Screw Kit
For Mounting Fan Blade Arm to Motor Housing



77040 - Polished Brass 77041 - Antique Brass 12 Fitter Screws
For Fan Lights



77015 Fan Blade Balancing Kit
Includes:
2-5 Gram Self-Adhering Weights
• 1 Balancing Clip



77059 Canopy Bracket
Black Finish
For Use With 1/2" or 3/4" I.D. Down Rods
Mounting Hardware Included



77058 For 1/2" I.D. Down Rods 77269 For 3/4" I.D. Down Rods Black Canopy Ball
Mounting Hardware Included



77016 20 - 1/2" Screws
Assorted for Fan Lights and Fan Blades
Includes:
• 5 - 8-32 Antique Brass Knurled Head Screws
• 5 - 8-32 Polished Brass Knurled Head Screws
• 5 - 10-24 Antique Brass Knurled Head Screws
• 5 - 10-24 Polished Brass Knurled Head Screws

*Bulk Pack

CARDED PRODUCT SOLD IN INNER PACK ONLY

www.westinghouselighting.com



77022
Fan
Light Switch
*Chrome Pull Chain,
2 Wire, Single Pole Switch
2' Braided Cord
3A, 250 VAC
6A, 125 VAC*



77023
Fan
Light Switch
*Polished Brass Pull Chain,
2' Braided Cord
3A, 250 VAC
6A, 125 VAC*



77287
Fan
Light Switch
*Antique Brass Pull Chain,
2' Braided Cord
3A, 250 VAC
6A, 125 VAC*



**77288 - Dual Capacitor,
3-Wire Unit**
3-Speed Fan Switch
*With Antique Brass
Pull Chain, 2' Braided Cord
3A, 250 VAC
6A, 125 VAC*



**77286 - Single Capacitor,
4-Wire Unit**
3-Speed Fan Switch
*With Antique Brass
Pull Chain, 2' Braided Cord
3A, 250 VAC
6A, 125 VAC*



**77075 - Triple Capacitor,
8-Wire Unit**
3-Speed Fan Switch
*With Polished Brass
Pull Chain, 2' Braided Cord
3A, 250 VAC
6A, 125 VAC*



**77021 - Single Capacitor,
4-Wire Unit**
3-Speed Fan Switch
*With Polished Brass
Pull Chain, 2' Braided Cord
3A, 250 VAC
6A, 125 VAC*




77270
48" Down Rod Wire
Extension Kit
*4 Wires with
4 Connectors*



77285
3-Way Fan
Light Switch
*3-Wire Unit
With Antique Brass
Pull Chain, 2' Braided Cord
3A, 250 VAC
6A, 125 VAC*



77052 - 3-Wire Unit
3-Way Fan
Light Switch
*With Polished Brass
Pull Chain, 2' Braided Cord
3A, 250 VAC
6A, 125 VAC*



77091
Fan Capacitor
*3 MFD and 6.5 MFD
3-Wire 150V*



ACCESSORIES

for ceiling fans & light fixtures

From product enhancing ceiling medallions to secure support braces and boxes, Westinghouse offers a full line of decorative and functional accessories to complement and complete any ceiling fan and light fixture installation.




Recessed Light Converter

Transform existing recessed lighting into a pendant or other light fixture!





O1011

- Quick and easy home upgrade with no remodeling
- Unique patent pending design
- Adjust to any recessed can size between 4" - 6" diameter
- No visible screws or hardware
- Perfect for hanging a pendant or other lighting fixtures
- Decorative medallion can be painted to match any decor
- Works with existing recessed cans that use medium base lamps*
- Can be used on sloped ceilings up to 45°
- 50 lb. maximum load rating



Note: Paintable decorative medallion and metal plate are optional when used on a 4" diameter recessed can.



* Converter works with existing recessed cans that use medium base PAR16, R16, A19, R20, PAR20, BR25, BR30, R30, PAR30, BR38, PAR38, BR40 or R40 lamps.

Easy-To-Install Elegance



CHOOSING A MEDALLION

Consider four factors when selecting the appropriate ceiling medallion.

FAN OR FIXTURE SIZE

- Medallions should be smaller or larger than the diameter of your ceiling fan or lighting fixture. They should not be the same size.

CEILING HEIGHT

- Higher ceilings can accommodate larger medallions.
- 28" or larger medallions complement a two-story foyer.

ROOM SIZE

- Large rooms accommodate large medallions.
- For a typical dining room with an 8' to 9' ceiling, an 18" to 26" diameter medallion works well.

MATERIAL

- Polyurethane medallions resemble traditional plaster medallions.
- Molded plastic medallions are lightweight and can be simply installed with adhesive.

PERSONALIZE YOUR DECORATIVE POLYURETHANE MEDALLION

- Lightweight polyurethane medallions can be installed finished or unfinished.
- Available in well-known architectural styles to complement molding or other architectural details.
- Installation hardware is included in all Westinghouse polyurethane ceiling medallions.
- For use with ceiling fans or lighting fixtures.
- Easily drilled or screwed.
- Will not warp, split or splinter.
- Easily caulked or spackled to hide installation hardware.



Polyurethane

Simply apply adhesive and screw or nail into any surface.



Polyurethane

Use unpainted or paint with any latex or oil based paint to create a look that matches any décor.

Polyurethane Medallions

Includes mounting hardware:

- 1 - 3" 1/8-IP nipple
- 2 - 2" 8-32 crossbar screws
- 3 - 1 1/2" - drywall screws



77754
White Finish
Cape May
Diameter: 28"
Center Opening: 4"



77750
White Finish
Bellezza
Diameter: 14"
Center Opening: 4"



77762
White Finish
Colonnade
Diameter: 12.38"
Center Opening: 4"



77757
White Finish
Sofia
Diameter: 21"
Center Opening: 4"



77756
White Finish
Francesca
Diameter: 18"
Center Opening: 4"



77752
White Finish
Soleil
Diameter: 20"
Center Opening: 4"



77764
Round Parisian Scroll
Antique Bronze Finish
Diameter: 16"
Center Opening: 4"

Molded Plastic

Adhesive or additional mounting hardware required.



77733
Round Beaded White Finish
 Diameter: 16"
 Center Opening: 4"



77732
Smooth White Finish
 Diameter: 16"
 Center Opening: 4"



77037
Smooth White Finish
 Diameter: 10"
 Center Opening: 4"




77027
Victorian White Finish
 Diameter: 10"
 Center Opening: 4"



77028
Victorian White Finish
 Diameter: 16"
 Center Opening: 4"



77035
Textured White Finish
 Diameter: 16"
 Center Opening: 4"



77034
Split Design White Finish
 Diameter: 16"
 Center Opening: 4"

Saf-T-Brace®

IDEAL FOR RETROFIT APPLICATION NO ATTIC ACCESS REQUIRED

- Fits 16" to 24" ceiling joists
- Patented design provides fast fingertip expansion and positive attachment to joists
- Fits all ceiling fans
- Position box anywhere along the brace
- For fixture support of 150 lbs. or less on 16" centers
- For fixture support of 50 lbs. or less on 24" centers
- Acceptable for fan support of 70 lbs. or less

Additional Security from Screw Connector

O1010

Saf-T-Brace®



Box Depth 1½"

Heavy Duty, 15.5 Cubic Inch Dual Mount Electrical Box*

6 Knockouts for Conduit or Romex

Individually Packaged, 24 Per Cut Case

Extra Strong Grip



PATENTED TECHNOLOGY

US PATENT NO.
4,909,405
4,659,051
5,860,548
DES.306,254



Step 1

Easy installation from below ceiling through any 4" diameter hole.

Step 2

Install end "A" by turning unit clockwise and applying pressure toward the ceiling joist.

Step 3

Slide unit toward other joist and again apply clockwise pressure.

Step 4

Attach electrical box and install fan or lighting fixture per manufacturer's instructions.

*Dual Mount = Box is threaded for 8-32 (ideal for box covers and light weight fixtures) and 10-24 screws (ideal for heavier fixtures and fans). Meets or Exceeds UL Standards Regarding Exposed Threads Within Box. Meets or Exceeds NEC Safety Codes.

Saf-T-Brace®

IDEAL FOR RETROFIT APPLICATION NO ATTIC ACCESS REQUIRED

- Fits 16" to 24" ceiling joists
- Patented design provides fast fingertip expansion and positive attachment to joists
- Fits all ceiling fans
- Position box anywhere along the brace
- For fixture support of 150 lbs. or less on 16" centers
- For fixture support of 50 lbs. or less on 24" centers
- Acceptable for fan support of 70 lbs. or less

Teeth Twist and Lock into Joist to Create More Secure Connection

01100

Saf-T-Brace®


Box Depth 1½"

Heavy Duty, 15.5 Cubic Inch Dual Mount* Electrical Box


6 Knockouts for Conduit or Romex

Individually Packaged, 24 Per Cut Case

Strong Grip




Saf-T-Brace® Display (18"L x 6 1/8"D x 8"H)
#01100DISP



new!


For more display information, contact your Westinghouse Sales Representative.

Includes Mounting Hardware & Instructions




Step 1

Easy installation from below ceiling through any 4" diameter hole.




Step 2

Rotate bar until teeth are fully embedded into joist.



Step 3

Attach electrical box and install fan or lighting fixture per manufacturer's instructions.



PATENTED
TECHNOLOGY

US PATENT NO.
5,720,461
5,860,548

*Dual Mount = Box is threaded for 8-32 (ideal for box covers and light weight fixtures) and 10-24 screws (ideal for heavier fixtures and fans). Meets or Exceeds UL Standards Regarding Exposed Threads Within Box. Meets or Exceeds NEC Safety Codes.

IDEAL FOR RETROFIT APPLICATION NO ATTIC ACCESS REQUIRED

- Fits 16" to 24" ceiling joists
- Patented design provides fast fingertip expansion and positive attachment to joists
- Fits all ceiling fans
- Position box anywhere along the brace
- For fixture support of 150 lbs. or less on 16" centers
- For fixture support of 50 lbs. or less on 24" centers
- Acceptable for fan support of 70 lbs. or less



Includes Larger Box for Increased Wire Capacity

01400

Saf-T-Brace®

Box Depth 2½"

Heavy Duty, 21.5 Cubic Inch Dual Mount Electrical Box
6 Knockouts for Conduit or Romex
Individually Packaged, 12 Per Cut Case
Strong Grip*




PATENTED TECHNOLOGY

US PATENT NO.
5,720,461
5,860,548


Step 1

Easy installation from below ceiling through any 4" diameter hole.




Step 2

Rotate bar until teeth are fully embedded into joist.



Step 3

Attach electrical box and install fan or lighting fixture per manufacturer's instructions.



*Dual Mount = Box is threaded for 8-32 (ideal for box covers and light weight fixtures) and 10-24 screws (ideal for heavier fixtures and fans). Meets or Exceeds UL Standards Regarding Exposed Threads Within Box. Meets or Exceeds NEC Safety Codes.

Saf-T-Bar®

IDEAL FOR NEW CONSTRUCTION ATTIC ACCESS REQUIRED

- Fits 16" to 24" ceiling joists
- Can be used with engineered truss
- Fits all ceiling fans
- Easy 4-step installation
- Position box anywhere along the brace
- For fixture support of 150 lbs. or less on 16" centers
- For fixture support of 90 lbs. or less on 24" centers
- Acceptable for fan support of 70 lbs. or less

Can be used with Engineered Truss

01525 & 0152511

Saf-T-Bar®

Box Depth 1½"

Heavy Duty, 15.5 Cubic Inch Dual Mount* Electrical Box


6 Knockouts for Conduit or Romex

01525 Individually Packaged, 12 Per Cut Case

0152511 Bulk Packed, 12 Per Cut Case



Includes Mounting Hardware & Instructions



Engineered Truss Application



Saf-T-Bar® Display (18"L x 6 1/8"D x 8"H)
#01525DISP



new!

For more display information, contact your Westinghouse Sales Representative.




PATENTED
TECHNOLOGY

US PATENT NO.
5,860,548

*Dual Mount = Box is threaded for 8-32 (ideal for box covers and light weight fixtures) and 10-24 screws (ideal for heavier fixtures and fans). Meets or Exceeds UL Standards Regarding Exposed Threads Within Box. Meets or Exceeds NEC Safety Codes.

HEAVY DUTY SUPPORT FOR NEW CONSTRUCTION OR FOR APPLICATIONS WHERE ATTIC IS ACCESSIBLE

- Includes mounting hardware and instructions
- For fixture support of 150 lbs. or less
- Acceptable for fan support of 70 lbs. or less



01020 & 0102011

Saf-T-Box®

*Fits All Ceiling Fans
3 Knockouts for Conduit or Romex
Box Depth 1½"*

Heavy Duty

*15.5 Cubic Inch Electrical Box
01020 Individually Packaged, 24 Per Cut Case
0102011 Bulk Packed, 48 Per Cut Case*



01050 & 0105011

Saf-T-Box®

3 Knockouts for Conduit or Romex

*1 Romex Clamp
Box Depth 1½"
Heavy Duty, 15.5 Cubic Inch
Dual Mount* Electrical Box*



010521

Saf-T-Box®

6 Knockouts for Conduit or Romex

*1 Romex Connector
Box Depth 1½"
Heavy Duty, 15.5 Cubic Inch
Dual Mount* Electrical Box*



0104011

Saf-T-Box®

**3 Knockouts for Conduit or Romex
1 Romex Clamp**

Box Depth 2½"
*Heavy Duty, 21.5 Cubic Inch
Dual Mount* Electrical Box*



PATENTED
TECHNOLOGY

US PATENT NO.
5,860,548

Sidemount Plus Fan Box®

IDEAL FOR REMODEL APPLICATIONS

- Sidemount bracket is removable for easy replacement of existing nail-on boxes without attic access
- Fits all ceiling fans
- Includes mounting hardware and instructions
- For fixture support of 70 lbs. or less
- Acceptable for fan support of 70 lbs. or less

Sidemount Plus Fan Box® Display (18"L x 6 1/8"D x 8"H)
#01240DISP



new!

For more display information, contact your Westinghouse Sales Representative.


8-32 threads for cover plates and lightweight lighting fixtures

1 Romex clamp

Saf-T-Cap® to protect bolts and wires during painting and sheetrock installation



10-24 threads for ceiling fans and chandeliers




Mounting hardware

01240 & 0124011

Sidemount Plus Fan Box®
3 Knockouts for Conduit or Romex
Box Depth 2 1/2"

Heavy Duty, 21.5 Cubic Inch
Dual Mount* Electrical Box
01240 Individually Packaged, 4 Per Cut Case
0124011 Bulk Packed, 12 Per Cut Case



8-32 threads for cover plates and lightweight lighting fixtures

1 Romex clamp

Saf-T-Cap® to protect bolts and wires during painting and sheetrock installation

10-24 threads for ceiling fans and chandeliers




Mounting hardware

Easy to Install through 4" Hole in Sheetrock


Step 1

Mount bracket to joist through 4" hole in sheetrock.



Step 2

Pull wire into box and remount box to bracket.



01250 & 0125011

Sidemount Plus Fan Box®
3 Knockouts for Conduit or Romex
Box Depth 1 1/2"

Heavy Duty, 15.5 Cubic Inch
Dual Mount* Electrical Box
01250 Individually Packaged, 24 Per Cut Case
0125011 Bulk Packed, 24 Per Cut Case



PATENTED TECHNOLOGY

US PATENT NO. 5,860,548

*Dual Mount = Box is threaded for 8-32 (ideal for box covers and light weight fixtures) and 10-24 screws (ideal for heavier fixtures and fans). Meets or Exceeds UL Standards Regarding Exposed Threads Within Box. Meets or Exceeds NEC Safety Codes.

IDEAL FOR NEW CONSTRUCTION OR REMODEL APPLICATIONS

- Fits all ceiling fans
- Includes mounting hardware and instructions
- For fixture support of 150 lbs. or less
- Acceptable for fan support of 70 lbs. or less

01030 & 0103011

Saf-T-Pan®


2 Knockouts for Conduit or Romex

Box Depth 5/8"

Heavy Duty, 8 Cubic Inch Dual Mount* Electrical Pan

01030 Individually Packaged, 24 Per Cut Case

0103011 Bulk Packed, 48 Per Cut Case



01036 & 0103611

Saf-T-Pan®

5 Knockouts for Conduit or Romex

Box Depth 1/2"

Heavy Duty, 6 Cubic Inch Dual Mount* Electrical Pan

01036 Individually Packaged, 12 Per Cut Case

0103611 Bulk Packed, 24 Per Cut Case



PATENTED TECHNOLOGY

US PATENT NO.
5,860,548



*Dual Mount = Box is threaded for 8-32 (ideal for box covers and light weight fixtures) and 10-24 screws (ideal for heavier fixtures and fans). Meets or Exceeds UL Standards Regarding Exposed Threads Within Box. Meets or Exceeds NEC Safety Codes.

Fan Master Jr.[®] & Fan Master[®]

IDEAL FOR NEW CONSTRUCTION APPLICATIONS

- Fits all ceiling fans
- 2 knockouts for Conduit or Romex
- Two hour fire rating
- Includes mounting hardware and instructions
- For fixture support of 150 lbs. or less
- Acceptable for fan support of 70 lbs. or less




0252511
Fan Master Jr.[®]
 Height 4"
 Box Depth ½"
13.4 Cubic Inch Wiring Capacity
 0252511 Bulk Packed, 12 Per Cut Case



Get the Wiring Space You Need... Where You Need It!



0200011
Fan Master[®]
 Height 4 13/16"
 Box Depth 5/8"
16.5 Cubic Inch Wiring Capacity
 0200011 Bulk Packed, 24 Per Cut Case




PATENTED TECHNOLOGY | US PATENT NO. 5,762,223


*Dual Mount = Box is threaded for 8-32 (ideal for box covers and light weight fixtures) and 10-24 screws (ideal for heavier fixtures and fans). Meets or Exceeds UL Standards Regarding Exposed Threads Within Box. Meets or Exceeds NEC Safety Codes.

SAFELY INSTALLS FANS AND FIXTURES IN SUSPENDED CEILING APPLICATIONS

- Reduce ceiling vibration and provide safe secure installation
- Fits 2' x 2' and 2' x 4' ceiling tile gridwork
- Position box anywhere along the brace
- Fits all ceiling fans
- For fixture support of 50 lbs. or less
- Acceptable for fan support of 50 lbs. or less



01070
Saf-T-Grid®
 Box Depth 1½"
 Heavy Duty, 15.5 Cubic Inch
 Dual Mount* Electrical Box
 6 Knockouts for Conduit or Romex
 Individually Packaged, 6 Per Cut Case



PATENTED TECHNOLOGY | US PATENT NO. 5,435,514 5,860,548

UL LISTED 85E6

*Dual Mount = Box is threaded for 8-32 (ideal for box covers and light weight fixtures) and 10-24 screws (ideal for heavier fixtures and fans). Meets or Exceeds UL Standards Regarding Exposed Threads Within Box. Meets or Exceeds NEC Safety Codes.



Westinghouse

INNOVATION YOU CAN BE SURE OF

GLASSWARE

assorted replacement glass & shades

Replacing broken glass, refreshing a luminaire or a ceiling fan is easy with our unique selection of glass. From classic glass diffusers to clip-on shades, we have something for everyone.



2¼" Fitter Glass

2¼" fitter glass is perfect for use with pendant, vanity fixtures and ceiling fans.

new!



*** 85651**
Imperial Jade
Neckless Shade
 Fitter: 2.25"
 Height: 5.88"
 Diameter: 4.88"

new!



*** 85734**
Devonshire
Linen Shade
 Fitter: 2.25"
 Height: 6.25"
 Diameter: 4.5"

new!



*** 85722**
White Opal
Fluted Shade
 Fitter: 2.25"
 Height: 5.5"
 Diameter: 4.75"

new!



*** 85723**
Amber Drum
Neckless Shade
 Fitter: 2.25"
 Height: 5.9"
 Diameter: 5.1"

new!



*** 81412**
Lunar Weave
Shade
 Fitter: 2.25"
 Height: 5.88"
 Diameter: 5.38"



*** 85703**
Honeycomb
Shade
 Fitter: 2.25"
 Height: 5.88"
 Diameter: 5.25"

new!



85702
Brushed Nickel Perforated
Metal Neckless Shade
 Fitter: 2.25"
 Height: 6.5"
 Diameter: 4.88"

new!



*** 85730**
Neckless Fire Pit
Long Shade
 Fitter: 2.25"
 Height: 8.5"
 Diameter: 4.5"

new!



*** 81631**
Caramel Swirl Long
Neckless Shade
 Fitter: 2.25"
 Height: 8.7"
 Diameter: 4.6"

new!



*** 85724**
Lunar Weave
Long Shade
 Fitter: 2.25"
 Height: 7.75"
 Diameter: 4.75"

2¼" Fitter Glass



* 81407
Garden Moss Shade
 Fitter: 2.25"
 Height: 5.25"
 Diameter: 4.5"



* 81310
Giraffe Spot Shade
 Fitter: 2.25"
 Height: 5.38"
 Diameter: 4.5"



* 81311
Fire Pit Shade
 Fitter: 2.25"
 Height: 5.38"
 Diameter: 4.5"




* 81409
Charcoal Swirl Shade
 Fitter: 2.25"
 Height: 5.25"
 Diameter: 4.85"



* 81400
Wildfire Cylinder Shade
 Fitter: 2.25"
 Height: 6.5"
 Diameter: 4.75"



* 81414
Linen Globe
 Fitter: 2.25"
 Height: 4.88"
 Diameter: 5.25"



* 81404
Marble Cylinder Shade
 Fitter: 2.25"
 Height: 6.5"
 Diameter: 4.75"



* 85701
Ice Cylinder Shade
 Fitter: 2.25"
 Height: 6.5"
 Diameter: 4.75"



* 85700
Amber Mist Cylinder Shade
 Fitter: 2.25"
 Height: 6.5"
 Diameter: 4.75"

*Hand blown glass

2¼" Fitter Glass



* 81410
Chocolate Drizzle Shade
 Fitter: 2.25"
 Height: 6.38"
 Diameter: 4.38"



* 81405
Van Gogh Shade
 Fitter: 2.25"
 Height: 6.25"
 Diameter: 4.38"



* 81413
Chili Pepper Shade
 Fitter: 2.25"
 Height: 6.25"
 Diameter: 4.38"



* 81315
Clear with Black Rope Shade
 Fitter: 2.25"
 Height: 5.75"
 Diameter: 4.63"



* 81314
Clear with White Rope Shade
 Fitter: 2.25"
 Height: 5.75"
 Diameter: 4.63"



* 81208
White Angled Design
 Fitter: 2.25"
 Height: 6.75"
 Diameter: 3.75"



* 81275
Indigo Blue Angled Design
 Fitter: 2.25"
 Height: 6.75"
 Diameter: 3.75"



* 81303
Amber and Brown Shade
 Fitter: 2.25"
 Height: 6.25"
 Diameter: 4.5"



* 81427
Spice Swirl Shade
 Fitter: 2.25"
 Height: 5.75"
 Diameter: 4.63"



* 81364
Temptress Red Shade
 Fitter: 2.25"
 Height: 5.25"
 Diameter: 4"

2¼" Fitter Glass



81279
Milky Scavo Bell
 Fitter: 2.25"
 Height: 5.13"
 Diameter: 5.13"



81098
Milky Scavo Bell
 Fitter: 2.25"
 Height: 5.25"
 Diameter: 5.5"



81257
Sandy Fluted Bell
 Fitter: 2.25"
 Height: 4.75"
 Diameter: 5.5"



81119
Licorice Marbleized Bell
 Fitter: 2.25"
 Height: 4.25"
 Diameter: 4.75"



81167
Brown Swirl Bell
 Fitter: 2.25"
 Height: 5.13"
 Diameter: 5.88"



81272
Milky Scavo Bell
 Fitter: 2.25"
 Height: 4.75"
 Diameter: 5.38"



* **81363**
Burnt Umber Swirl Bell
 Fitter: 2.25"
 Height: 4.81"
 Diameter: 5.38"



81265
Hand-Painted Leaf Design Bell
 Fitter: 2.25"
 Height: 4.75"
 Diameter: 5.38"



81121
Square Tiffany Shade
 Fitter: 2.25"
 Height: 5.13"
 Width: 4.75"



* **81356**
Tortoise Bell
 Fitter: 2.25"
 Height: 5.25"
 Diameter: 4.75"

*Hand blown glass

2¼" Fitter Glass



*** 81353**
Clear and White Design Bell
 Fitter: 2.25"
 Height: 4.75"
 Diameter: 5"



81422
Brown Marbleized Bell
 Fitter: 2.25"
 Height: 4.75"
 Diameter: 5.38"



81391
Antique Smolder Bell
 Fitter: 2.25"
 Height: 4.75"
 Diameter: 5.25"



81333
Honey Swirl Scavo Shade
 Fitter: 2.25"
 Height: 4.38"
 Diameter: 6.88"



81355
Clear Prismatic Shade
 Fitter: 2.25"
 Height: 3.75"
 Diameter: 6.5"



81120
Cappuccino Swirl Shade
 Fitter: 2.25"
 Height: 4.25"
 Diameter: 6.88"



81365
Parchment Leaf Shade
 Fitter: 2.25"
 Height: 4.5"
 Diameter: 6"



81382
Linen Pendant Shade
 Fitter: 2.25"
 Height: 5"
 Diameter: 7.75"



81135
Amber Swirl Shade
 Fitter: 2.25"
 Height: 5"
 Diameter: 7.75"



*** 81375**
Tortoise Pendant Shade
 Fitter: 2.25"
 Height: 5"
 Diameter: 7.5"

2¼" Fitter Glass



81411
Satin Etched Tulip Shade
 Fitter: 2.25"
 Height: 5"
 Diameter: 4.25"



81270
**Frosted and Clear
 Cross Shade**
 Fitter: 2.25"
 Height: 5.25"
 Diameter: 5"



81099
Etched Clear Shell Bell
 Fitter: 2.25"
 Height: 5"
 Diameter: 4.75"



81051
Frosted Etched Bell
 Fitter: 2.25"
 Height: 4.5"
 Diameter: 4.75"



*** 81227**
White Opal Bell
 Fitter: 2.25"
 Height: 4.75"
 Diameter: 5.12"



81097
Frosted Pleated Shade
 Fitter: 2.25"
 Height: 4.75"
 Diameter: 4"



81067
Frosted Beaded Bell
 Fitter: 2.25"
 Height: 3.75"
 Diameter: 4.75"



81253
**Frosted Bell with
 Clear Square Design**
 Fitter: 2.25"
 Height: 4.63"
 Diameter: 5.38"



81072
**Frosted and Clear
 Stripe Shade**
 Fitter: 2.25"
 Height: 3.75"
 Diameter: 4.63"



81277
**Beveled Clear
 Glass Bell**
 Fitter: 2.25"
 Height: 4.75"
 Diameter: 4.75"



*** 81095**
Clear Seeded Bell
 Fitter: 2.25"
 Height: 4.62"
 Diameter: 5"

*Hand blown glass

2¼" Fitter Glass



81258
Clear Ribbed Bell
 Fitter: 2.25"
 Height: 4.5"
 Diameter: 4.75"



81066
Frosted Ribbed Bell
 Fitter: 2.25"
 Height: 4.5"
 Diameter: 4.75"



81479
**Crystal Clear
 Pleated Shade**
 Fitter: 2.25"
 Height: 5"
 Diameter: 4.25"



81094
**Frosted Pleated
 Shade**
 Fitter: 2.25"
 Height: 5"
 Diameter: 4.25"



81096
Frosted Pleated Bell
 Fitter: 2.25"
 Height: 5"
 Diameter: 4.25"



81242
Satin Crimp Shade
 Fitter: 2.25"
 Height: 4.13"
 Diameter: 5"



* **81282**
**Frosted Etched Grape
 Design Crimp Shade**
 Fitter: 2.25"
 Height: 4.81"
 Diameter: 4.25"



* **81082**
**Clear and Frosted with
 Gold Band Crimp Shade**
 Fitter: 2.25"
 Height: 5.12"
 Diameter: 5.75"

Glass Diffusers



81720
White Diffuser
 Square: 12"
 Depth: 1.5"

81800
**Clear Wheat Design
 on White Ruffled
 Edge Diffuser**
 Square: 12"
 Depth: 1.5"

81807
**Clear Floral Design
 on White Diffuser**
 Square: 12"
 Depth: 1.5"

81810
**Clear Floral Design
 on White Diffuser**
 Square: 14"
 Depth: 1.75"



81727
**Gloss White
 Diffuser**
 Diameter: 12"
 Depth: 1.75"



81925
**White Smooth
 Scavo Diffuser**
 Diameter: 13"
 Depth: 1.75"



81819
**Clear Dot Pattern
 Diffuser**
 Diameter: 13"
 Depth: 1.25"



81805
**Clear Dot Pattern
 Diffuser**
 Diameter: 15"
 Depth: 1.5"



81770
**Clear Wheat Design
 on White Diffuser**
 Diameter: 13"
 Depth: 2.13"



81750
**Clear Wheat Design
 on White Diffuser**
 Diameter: 12"
 Depth: 1.75"



81837
Frosted Diffuser
 Diameter: 13"
 Depth: 2.31"

Glass Diffusers



*** 81578**
Opal
Schoolhouse Shade
 Fitter: 4"
 Height: 6.25"
 Diameter: 7.25"

*** 85578**
6-Pack of 81578



*** 81528**
Opal
Schoolhouse Shade
 Fitter: 4"
 Height: 7"
 Diameter: 8.5"

*** 85528**
6-Pack of 81528



*** 81592**
White
Schoolhouse Shade
 Fitter: 3.25"
 Height: 4.94"
 Diameter: 5.75"



*** 81290**
Schoolhouse with Ridged
Design Shade
 Fitter: 4"
 Diameter: 8"



*** 81620**
Grape Satin
Mushroom Shade
 Fitter: 6"
 Height: 3.5"
 Diameter: 8"



*** 83757**
White Mushroom Shade
 Fitter: 8"
 Height: 4"
 Diameter: 9.5"

*** 85757**
6-Pack of 83757



*** 81613**
White Mushroom Shade
 Fitter: 6"
 Height: 3.75"
 Diameter: 7.5"

*** 85613**
6-Pack of 81613



81606
White and Clear
Drum Shade
 Fitter: 6"
 Height: 3.38"
 Diameter: 6.5"

85606
6-Pack of 81606



85608
White and Clear
Drum Shade
 Fitter: 8"
 Height: 4"
 Diameter: 8.75"
 Sold as 6-Pack Only



81609
White and Clear
Drum Shade
 Fitter: 10"
 Height: 4.25"
 Diameter: 11"

Chimneys



* 81170
Clear Flare Shade
 Fitter: 1.63"
 Height: 8"
 Diameter: 4.88"



* 81162
**Clear Williamsburg
 Style Shade Shade**
 Fitter: 1.63"
 Height: 6.5"
 Diameter: 3.75"



* 81112
**Clear Stenciled
 Grape Design Shade**
 Fitter: 1.63"
 Height: 6"
 Diameter: 3.75"



* 81169
Clear Flare Shade
 Fitter: 1.63"
 Height: 6.75"
 Diameter: 3.75"



* 81160
Clear Flare Shade
 Fitter: 1.63"
 Height: 6.5"
 Diameter: 3.63"



* 83072
Clear Glass Chimney
 Fitter: 2.63"
 Height: 10"
 Bulge: 3.63"
 Top Opening: 2"



* 83073
3/4 Frosted Glass Chimney
 Fitter: 2.63"
 Height: 10"
 Bulge: 3.63"
 Top Opening: 2"



* 83062
Clear Glass Chimney
 Fitter: 2.63"
 Height: 8"
 Bulge: 3.5"
 Top Opening: 1.63"



* 83063
3/4 Frosted Glass Chimney
 Fitter: 2.63"
 Height: 8"
 Bulge: 3.5"
 Top Opening: 1.63"

*Hand blown glass

Chimneys



* **83070**
Clear Glass Chimney
 Fitter: 2.63"
 Height: 8.5"
 Bulge: 3.63"
 Top Opening: 2"



* **83071**
¾ Frosted Glass Chimney
 Fitter: 2.63"
 Height: 8.5"
 Bulge: 3.63"
 Top Opening: 2"



* **83100**
Clear Glass Chimney
 Fitter: 3"
 Height: 10"
 Bulge: 4"
 Top Opening: 2"



* **83101**
¾ Frosted Glass Chimney
 Fitter: 3"
 Height: 10"
 Bulge: 4"
 Top Opening: 2"



* **83090**
Clear Glass Chimney
 Fitter: 3"
 Height: 8.5"
 Bulge: 4"
 Top Opening: 2"



* **83091**
¾ Frosted Glass Chimney
 Fitter: 3"
 Height: 8.5"
 Bulge: 4"
 Top Opening: 2"



* **83102**
Clear Glass Chimney
 Fitter: 3"
 Height: 10"
 Bulge: 3.63"
 Top Opening: 2"



* **83103**
¾ Frosted Glass Chimney
 Fitter: 3"
 Height: 10"
 Bulge: 3.63"
 Top Opening: 2"



* **83112**
Clear Glass Chimney
 Fitter: 3"
 Height: 11.75"
 Bulge: 3.63"
 Top Opening: 1.88"



* **83131**
Clear Glass Chimney
 Fitter: 3"
 Height: 14"
 Bulge: 3.63"
 Top Opening: 2"

Glass Globes 3¼" & 4" Fitters

85612

**Frosted and Clear
Shade**

Fitter: 3.25"

Height: 5"

Diameter: 6"

Sold as 6-Pack Only



81602

Clear Design Shade

Fitter: 3.25"

Height: 5.75"

Diameter: 5.5"



85602

6-Pack of 81602

*** 85705**

Smoke Lustre Globe

Fitter: 3.25"

Diameter: 6"

Sold as 6-Pack Only



81254

**Clear Prismatic
Globe**

Fitter: 3.25"

Diameter: 6.38"



85254

6-Pack of 81254

81338

**Clear Prismatic
Globe**

Fitter: 4"

Diameter: 8"



*** 81549**

Gloss Clear Globe

Fitter: 4"

Diameter: 7.5"



85338

6-Pack of 81338

*** 81558**

Gloss Smoke Globe

Fitter: 4"

Diameter: 7.5"



*** 81712**

**Gloss Clear Lustre
Globe**

Fitter: 3.25"

Diameter: 6"



*** 85712**

4-Pack of 81712

**Hand blown glass*

Glass Globes 3¼" & 4" Fitters

- * 81501
Opal Globe
Fitter: 3.25"
Diameter: 6"



- * 81570
Gloss White Globe
Fitter: 3.25"
Diameter: 6"



- * 85570
6-Pack of 81570

- * 81504
Opal Globe
Fitter: 4"
Diameter: 8"



- * 81571
Gloss White Globe
Fitter: 4"
Diameter: 8"



- * 85571
6-Pack of 81571

- * 81575
Frosted Victorian
Globe
Fitter: 4"
Diameter: 7.5"



- * 81707
Victorian Globe
Fitter: 3.25"
Diameter: 6"



- * 85707
6-Pack of 81707

- * 81560
Clear Seeded
Globe
Fitter: 3.25"
Diameter: 6"



- * 81574
Cloudy Frosted
Globe
Fitter: 3.25"
Diameter: 6"



Polycarbonate and Acrylic Shades

81918

**Drum Lens White
Acrylic Shade**

Notched Fitter: 9.88"

Height: 2.5"

Diameter: 11"



81883

**White Acrylic
Neckless Globe**

Diameter: 12"

Opening: 5.25"



81893

**White Polyethylene
Neckless Globe**

Diameter: 12"

Opening: 5.25"

81919

**Drum Lens White
Acrylic Shade**

Fitter: 12.63"

Height: 2.5"

Diameter: 13.75"



81884

Diameter: 14"

Opening: 5.25"

81896

Diameter: 16"

Opening: 5.25"



81450

**White Glass
Threaded Neck Globe**

Thread: 3.25"

Diameter: 6"



81905

**White Polyethylene
Globe**

Fitter: 3"

Diameter: 6"



81900

**White Acrylic
Globe**

Fitter: 4"

Diameter: 8"



81869

**White Polycarbonate
Globe**

Fitter: 3.25"

Diameter: 6"

85450

6-Pack of 81450



81890

Fitter: 4"

Diameter: 10"

81901

Fitter: 4"

Diameter: 10"

85869

6-Pack of 81869

81877

**White Polycarbonate
Threaded Neck Globe**

Thread: 3.25"

Diameter: 6"

81892

Fitter: 4"

Diameter: 12"

81902

Fitter: 4"

Diameter: 11"

85888

Fitter: 4"

Diameter: 8"

Sold as 6-Pack Only

81887

Thread: 3.25"

Diameter: 6"

Glass, Polycarbonate and Acrylic Shades



81876
**Clear Tapered Polycarbonate
 Threaded Neck Shade**
Thread: 3.25"
Height: 8.75"
Diameter: 4"



81456
**Vapor Proof Clear Optic
 Glass Threaded Neck Shade**
Thread: 3.25"
Height: 6.75"
Diameter: 3.5"



81448
**Vapor Proof Clear Glass
 Threaded Neck Shade**
Thread: 3.25"
Height: 6.75"
Diameter: 3.5"



81452
**Vapor Proof Clear Glass
 Threaded Neck Shade**
Thread: 3.25"
Height: 6"
Diameter: 3.5"



81451
**White Glass Threaded
 Neck Shade**
Thread: 3.25"
Height: 6.25"
Diameter: 3.5"

85451
6-Pack of 81451



81920
**Polycarbonate Threaded
 Neck Shade**
Thread: 3.25"
Height: 5.5"
Diameter: 3.63"



81457
**White Tapered Polycarbonate
 Threaded Neck Shade**
Thread: 3.25"
Height: 8.5"
Diameter: 4"



81459
**White Tapered Polycarbonate
 Threaded Neck Shade**
Thread: 3.25"
Height: 6.25"
Diameter: 4"

Assorted Glass Fitters And Channels



*** 81104**
Frosted Etched Shade
 Fitter: 1.63"
 Height: 5.25"
 Diameter: 4.5"



*** 81100**
Frosted Etched Shade
 Fitter: 1.63"
 Height: 5"
 Diameter: 4.25"



*** 81151**
Satin White Shade
 Fitter: 2"
 Height: 5"
 Diameter: 4.75"

*** 85100**
6-Pack of 81100

*** 85151**
6-Pack of 81151



81590
Satin Floral Etched Design Shade
 Fitter: 3.25"
 Height: 4.25"
 Diameter: 7"

81617
Clear Shade
 Fitter: 3.25"
 Height: 4.75"
 Diameter: 3.63"



85617
6-Pack of 81617



81604
White Grooves with Clear Bottom Shade
 Fitter: 3.25"
 Height: 4.5"
 Length: 5.75"

85604
6-Pack of 81604

*** 81230**
Green with White Interior Shade
 Height: 3.13"
 Width: 8.75"
 Depth: 5"
 1/2" holes on both sides



81760
White Channel
 Length: 24"
 Width: 3.75"
 Depth: 3"
 Hole Size: .38"
 2 Holes
 6 1/2" from ends
 11" between holes



81764
White Channel
 Length: 15"
 Width: 3.75"
 Depth: 3"
 Hole Size: .38"
 Centered Hole



81759
White Channel
 Length: 12"
 Width: 3.75"
 Depth: 3"
 Hole Size: .38"
 Centered Hole





81758
White Channel
 Length: 7.5"
 Width: 3.75"
 Depth: 3"
 Hole Size: .38"
 Hole 1.75" from end



*Hand blown glass

Clip-On Shades



No wiring.
No tools.
Simply clip onto an A shape bulb. 

Porcelain lamp holder shown (Item #22745) can be found on page 168. (Sold separately.)

Create a Fixture Instantly!

Clip-on shades are a quick and easy way to change a light bulb into a fixture! Instantly add a decorative touch!



81514
Acrylic White Dome
Clip-On Shade with
Pull Chain Opening
Height: 4.75"
Diameter: 7.75"



81499
Polypropylene Satin Tulip
Clip-On Shade
Height: 4.75"
Diameter: 8"




81493
Acrylic Prismatic Dome
Clip-On Shade
Height: 4.75"
Diameter: 8"



81494
Acrylic White Dome
Clip-On Shade
Height: 4.75"
Diameter: 7.75"

Glassware Glossary



FITTER (F)

Fitter size is the diameter of the glass where the glass attaches to the fixture or lamp.

HEIGHT (H)

Distance between the two farthest points opposite each other on the top and bottom of the glass that form a vertical line.

DIAMETER (D)

Distance between two opposite points at the widest part of the glass that form a horizontal line.

NECKLESS

A piece of glass without a neck.

CENTER HOLE

The opening on a neckless shade and measured like a fitter. If a piece of glass has a fitter and a center hole, the center hole is used for lock-up.

DEPTH

Distance from the center point inside the glass to the point directly opposite, this is measured without mounting.

BULGE

The diameter measured at the widest part of a chimney.

TOP OPENING

Distance between the two farthest points opposite each other on the top of a student shade. All top openings are wide enough and made to fit over the average chimney.

THREADED NECK

A fitter that attaches to the fixture or lamp by means of threads in the glass.

NOTCHED FITTER

Designed to lock tightly into specially designed holders with $\frac{1}{4}$ turn.

Plastic Material Guide

Feature Comparison Chart

Feature	Polyethylene	Acrylic	Polycarbonate
Heat Resistance	G	G	E
Quality of Seams	F	E	E
UV Resistance	F	E	F
Strength	G	G	E
Light Transmission	F	E	G
Wall Thickness Uniformity	G	G	E
Shatter Resistance	E	F	G
Surface Characteristics	G	E	G
Appearance vs. Time	G	E	G
Strength vs. Time	G	E	F
Overall Appearance	G	E	G

KEY:

E = Excellent

G = Good

F = Fair

Recommended Maximum Incandescent Wattage Ratings

Polyethylene		Acrylic		Polycarbonate	
Globe	Watts	Globe	Watts	Globe	Watts
6"	40	6"	60	6"	75
8"	75	8"	75	Cylinder	Watts
10"	100	10"	100	5½"	60
12"	150	12"	150	5¾"	60
14"	200	14"	150	6¼"	60
16"	200	16"	200	7¼"	60
18"	250	18"	200	8½"	60
—	—	Cylinder	Watts	8¾"	60
—	—	5"	60	—	—

This wattage guide is a general recommendation only. Actual wattage ratings are influenced by fixture type, bulb location and ambient temperature. The light source should be located at the center of each shade.

LIGHTING HARDWARE

bulk & packaged

For every repair need, Westinghouse has you covered. From sockets to switches, canopies to crossbars, we have those hard to find parts to make your life easier.



Hardware comes either in retail package or bulk pack. Bulk pack has been indicated throughout the section.

Glass Shade Holder Kits & Accessories

Glass Shade Holder Kits

3/4" Holder

Use (1) Medium Base Lamp, 60 Watt Maximum

Includes:

- 1 Crossbar
- 2 Mounting Screws
- 1 Green Grounding Screw
- 3 Knurled Fitter Screws
- 1 Fiberglass Insulator



70042
Shade Holder with Polarized Convenience Outlet
Chrome Finish



70229 - Antique Brass Finish
70242 - Brass Finish
70244 - White Finish
Shade Holder with On/Off Pull Chain Switch



70230 - Brass Finish
70236 - Antique Brass Finish
70240 - Chrome Finish
Shade Holder

70234
Twin Cluster Ceiling Kit
Medium Base

Includes:

- 1 Canopy
- 1 Wired Socket
- 1 Crossbar
- 2 Mounting Screws
- 1 Lock-Up Cap
- 2 Rubber Washers
- Ideal for Glass Diffusers



*** 22745**
Porcelain Lamp Holder
Keyless
Medium Base
660 Watts Max., 250 Volts
8-32 Screws
Height - 1 3/4"



70241 - Chrome Finish
70231 - Brass Finish
70243 - Antique Brass Finish
70238 - White Finish
4" Holder
Use (1) Medium Base Lamp, 60 Watt Maximum

70414
Twin Cluster
Medium Base
24" Wire Leads
Tapped Both Ends
660 Watts Max.
250 Volts
1/8-IP Female Threads
Height - 3 1/4"



*** 22259**
Twin Cluster Socket with Male Threads on Each End
6" Wire Leads
18 Gauge, 105° Leads
660 Watts Max.
250 Volts
1/8-IP Nipple
Height - 4 1/2"



*** 22256**
3 Light Cluster with Male Threads on Each End
6" Wire Leads
18 Gauge
105° Leads
660 Watts Max.
250 Volts
1/8-IP Nipple
Height - 4 3/4"



*Bulk Pack

CARDED PRODUCT SOLD IN INNER PACK ONLY

www.westinghouselighting.com

Sockets



***22207**
2-Piece Phenolic Shell
 On/Off
 Medium Base
 Nipple 1/8"-IP
 250 Watts Max.
 250 Volts
 Height - 2 3/4"



***22205**
1-Piece Phenolic Shell
 Bottom Turn Knob Socket
 Medium Base
 Nipple 1/8"-IP
 660 Watts Max.
 250 Volts
 Height - 3 1/4"



***22234**
High Heat Phenolic On/Off
 Medium Base
 Keyless
 Bushing 1/8"-IP with Set Screw
 660 Watts Max.
 250 Volts
 Height - 2 3/4"



***22237**
Push-Through Phenolic
 Medium Base
 1/8"-IP Cap with Side Screw
 Aluminum Screw Shell
 600 Watts Max.
 250 Volts
 Height - 2 5/8"



70146
Vertical Phenolic Snap-In Socket
 Fits into 3/8" x 1/4" Hole
 Medium Base
 660 Watts Max.
 250 Volts



70407
Keyless Phenolic Socket
 1/8"-IP Hickey
 Medium Base
 660 Watts Max.
 250 Volts



70430
Turn Knob Phenolic Socket
 On/Off
 Threaded 1/8"-IP
 Medium Base
 660 Watts Max.
 250 Volts



70433
Pull Chain Phenolic Socket
 On/Off
 Tapped 1/8"-IP
 Medium Base
 250 Watts Max.
 250 Volts



70145
Horizontal Phenolic Snap-In Socket
 Fits into 7/8" x 1/4" Hole
 Medium Base
 660 Watts Max.
 250 Volts



***22501**
Push-Through
 Medium Base
 660 Watts Max.
 250 Volts
 Height - 1 1/16"



***22503**
Pull Chain
 On/Off
 Medium Base
 250 Watts Max.
 250 Volts
 Height - 1 3/4"



***22502 - On/Off**
***22504 - 3-Way**
***22505 - 2-Circuit Turn Knob**
 Medium Base
 250 Watts Max.
 250 Volts
 Height - 1 1/16"


***Bulk Pack**
www.westinghouselighting.com

CARDED PRODUCT SOLD IN INNER PACK ONLY



*** 22381 - 3 Light**
*** 22382 - 4 Light**
Black Harness Set

Candelabra Base
 Fits 3/4" Hole
 Includes Lock Nuts
 SPT-2, 18 Gauge,
 105° Leads
 75 Watts Max.
 Per Socket
 125 Volts
 6 1/4" Between Sockets
 12" on End Height - 1 1/4"



*** 22380**
1 Light
Harness Set

Candelabra Base
 Fits 3/4" Hole
 Includes Lock Nut
 12" Wire Leads
 SPT-2, 18 Gauge,
 105° Leads
 75 Watts Max., 125 Volts
 Height - 1 1/4"



*** 22377 - 18" Leads**
Candelabra Base

1/8-IP Hickey
 18 Gauge, 105° Leads
 75 Watts Max., 125 Volts
 Height - 1 1/4"



*** 22221**
Pigtail Holder

6" Wire Leads
 Medium Base
 14 Gauge 105° Leads
 660 Watts Max., 250 Volts
 Height - 1 1/2"



*** 22220**
Pigtail

24" Wire Leads
 Candelabra Base
 18-2, SPT-1
 105° Leads
 75 Watts Max.
 Height - 1 1/8"



*** 22223**
Snap-In Pigtail

24" Wire Leads
 Candelabra Base
 Snaps Into
 1" Diameter Hole
 18-2, SPT-1, 105° Leads
 75 Watts Max.
 Height - 1 1/8"



*** 22215**
Medium Base

6" Wire Leads and
 Straight Bracket
 18 Gauge, 105° Leads
 Bracket Extends 1 1/8"
 Measured Center
 to Center
 660 Watts Max.
 250 Volts
 Height - 1 1/2"



*** 22203**
Medium Base

1/8-IP Hickey
 660 Watts Max.
 250 Volts
 Height - 2"



*** 22200**
Pin Type With Cap

Candelabra Base
 Use with SPT-1 Wire
 75 Watts Max.
 125 Volts
 Height - 1 1/4"



*** 22213**
Medium Base

6" Wire Leads
 Fits 1 1/4" Hole
 18 Gauge, 105° Leads
 660 Watts Max.
 250 Volts
 Height - 1 1/2"



*** 22214**
Medium Base

6" Wire Leads and
 Ground Wire
 Fits 3/8" x 1/4" Hole
 18 Gauge, 105° Leads
 660 Watts Max.
 250 Volts
 Height - 2"



*** 22217**
Medium Base

9" Wire Leads
 Fits 3/8" x 1/4" Hole
 18 Gauge, 105° Leads
 660 Watts Max.
 250 Volts
 Height - 1 1/2"



*** 22216**
Medium Base

9" Wire Leads
 1/8-IP Hickey
 18 Gauge, 105° Leads
 660 Watts Max.
 250 Volts
 Height - 1 1/8"



*** 22222**
Pin-Type Socket

Medium Base
 Use with SPT-2 Wire
 660 Watts Max.
 250 Volts
 with Hanger Bracket
 Height - 2"

*Bulk Pack

CARDED PRODUCT SOLD IN INNER PACK ONLY

www.westinghouselighting.com

Sockets



70412 - 3-Way
70413 - On/Off
70421 - 2 Circuit
Turn-Knob Socket
 Brass Finish
 Medium Base
 Tapped 1/8-IP
 250 Watts Max., 250 Volts



70410 - Brass Finish
22011 - Polished Brass
22013 - Brass Finish
Push-Through Socket
 with Set Screw
 On/Off
 Brass Finish
 Medium Base
 Tapped 1/8-IP
 660 Watts Max., 250 Volts




70411 - On/Off
 250 Watts Max., 250 Volts
70431 - 3-Way
 250 Watts Max., 250 Volts
Pull Chain Socket
 Brass Finish
 Medium Base
 Tapped 1/8-IP




70417
Quick-Snap Socket
 3-Way Turn Knob
 Brass Finish
 Medium Base
 Tapped 1/8-IP
 250 Watts Max., 250 Volts




* **22001 - Brite Gilt**
 * **22003 - Brass Finish**
Keyless
 Medium Base
 Bushing 1/8-IP with Set Screw
 660 Watts Max., 250 Volts
 Height - 2"



* **22031 - Polished Brass**
 * **22033 - Brass Finish**
Turn Knob
 Medium Base
 Bushing 1/8-IP with Set Screw
 Removable Knob
 250 Watts Max., 250 Volts
 Height - 2 1/2"



* **22041 - Polished Brass**
3-Way Turn Knob
 Medium Base
 Bushing 1/8-IP with Set Screw
 Removable Knob
 250 Watts Max., 250 Volts
 Height - 2 1/2"



* **22051 - Polished Brass**
 * **22053 - Brass Finish**
2 Circuit Turn Knob
 Medium Base
 Bushing 1/8-IP with Set Screw
 Removable Knob
 250 Watts Max., 250 Volts
 Height - 2 1/2"



70161
Two Replacement Knobs
 Black Finish
 With 1/2" Extensions
 Tapped 3/16-F x 3/16-M



* **22551**
Replacement Paper Shell
 For Turn Knob or
 Pull Chain Sockets



* **22517**
Brass Special Cap
 1/4-IP Thread with
 Set Screw



70160
Two Socket Keys
 Brass Finish
 With 1/2" Extensions
 Tapped 3/16-F x 3/16-M



*** 22135**
70405 (Carded 2-Pack)
2" Keyless Socket
 Medium Base
 1/8-IP Threaded Hickey
 660 Watts Max., 250 Volts



*** 22136**
3" Keyless Socket
 Medium Base
 1/8-IP Hickey
 660 Watts Max., 250 Volts
 Height - 3"



*** 22125**
Candelabra Base
 1/8-IP Hickey
 75 Watts Max., 125 Volts
 Height - 1 1/2"



*** 22126**
70403 (Carded 2-Pack)
2" Keyless Socket
 Candelabra Base
 1/8-IP Threaded Hickey
 75 Watts Max., 125 Volts



*** 22138**
70404 (Carded 2-Pack)
Adjustable Keyless Socket
 Medium Base
 1/8-IP Hickey
 660 Watts Max., 250 Volts
 Height Adjustable from 4" - 5 5/8"



*** 22127**
70402 (Carded 2-Pack)
Adjustable Keyless Socket
 Candelabra Base
 1/8-IP Threaded Hickey
 75 Watts Max., 125 Volts
 Height Adjustable from 3 1/4" - 4 3/4"

*Bulk Pack

CARDER PRODUCT SOLD IN INNER PACK ONLY

www.westinghouselighting.com

Porcelain Fixture Sockets

70419

Porcelain Socket

*Candelabra Base
10" Wire Leads
Height - 1 7/8"
Diameter - 1"
1/8-IP Hickey, 18 Gauge
105° Leads
75 Watts Max., 125 Volts*



70409

Porcelain Keyless Socket

*Medium Base
1/8-IP Threaded Cap
660 Watts Max.
250 Volts
Height - 2"*



70408

Porcelain Keyless Socket Adapter Kit

*1/8-IP Threaded Cap
660 Watts Max.
250 Volts*



Includes:

- 1 Medium Base Socket
- 1 Screw Collar Loop
- 1 Fiber Washer
- 1 Locknut
- 1/8-IP x 1" Nipple
- 1/8-IP x 2" Nipple



*** 22370**

77077

70425

Porcelain Fixture Socket

*Medium Base
10" Wire Leads
1/8-IP Hickey
18 Gauge, 105° Leads
660 Watts Max., 250 Volts
Height - 2"*

*** 22212**

70424

Porcelain Snap-In Socket

*Medium Base
Fits 1 1/2" Hole
6" Wire Leads
18 Gauge, 125° Leads
660 Watts Max., 250 Volts
Height - 1 3/4"*

70420

Porcelain Threaded Socket

*Medium Base
Copper Alloy
Nickel-Plated, Screw
Shell, Screw Terminals
2 Captive 6-32 Screws
660 Watts Max., 250 Volts,
Height - 1 3/4"*



*** 22272**

70429

Porcelain Threaded Socket with Steel Shade Ring

*Medium Base
Bushings 1/8-IP with Set Screw
660 Watts Max., 250 Volts
Height - 2 1/8"
Ring Size - 2 5/8"*

*** 22371**

70426

Porcelain Fixture Socket

*Medium Base
1/4-IP Hickey
660 Watts Max.
250 Volts
Height - 2"*

70010

Porcelain Threaded Socket with Aluminum Shade Ring

*Medium Base
660 Watts Max.
250 Volts
Height - 1 5/8"
Ring Height - 1/2"*

***Bulk Pack**

www.westinghouselighting.com

CARDED PRODUCT SOLD IN INNER PACK ONLY



*** 22264**
Receptacle
 Candelabra Base
 75 Watts Max., 125 Volts
 Height - 7/8"



*** 22273**
One-Piece Receptacle
 Medium Base
 600 Watts Max., 250 Volts
 Height - 1/2"
 180° C Maximum Temp.



*** 22150**
70364
Socket Extender
 Medium Base
 660 Watts Max., 250 Volts
 Extension - 1/4"
 Overall Length - 2/4"



*** 22218**
Keyless Socket
1 Screw Surface Mount
 Medium Base
 7" Wire Leads
 660 Watts Max., 250 Volts
 105° Leads
 Leads Height - 1 5/8"



*** 22372**
Socket
 Medium Base
 9" Wire Leads
 Fits 3/8" x 1/4" Hole
 18 Gauge, 105° Leads
 660 Watts Max., 250 Volts
 Height - 2"



*** 22276**
Snap-In
Porcelain Socket
 660 Watts Max., 250 Volts
 Height - 1 3/4"



*** 22281**
Mogul Base Socket
 3-Way
 Removable Knob
 Bushing 1/4-IP
 750 Watts Max., 250 Volts
 Height - 4/4"



*** 22282**
Mogul Base Socket
 1500 Watts Max., 600 Volts
 Height - 2 5/8"
 4KV Pulse Rating



*** 22266**
70423
Two-Piece
Sign Receptacle
 Medium Base
 660 Watts Max., 250 Volts
 Height - 1 1/2"
 300° C Maximum Temp.

*Bulk Pack

CARDED PRODUCT SOLD IN INNER PACK ONLY

www.westinghouselighting.com



*** 16074
70428**
**Steel Shade Ring
For Medium Base Sockets**
Ring Size - 2³/₈"
Outside Diameter - 2¹/₄"
Inside Diameter - 1¹/₂"



70001
**Two Aluminum Shade Rings
For Medium Base Sockets**
Outside Diameter - 2"
Inside Diameter - 1¹/₂"



70435
**Phenolic Shade Ring
For Medium Base Sockets**
Outside Diameter - 2³/₁₆"
Inside Diameter - 1¹/₈"



*** 22274**
Keyless Twin Socket
Medium Base
Bushing 1/8"-IP
With Set Screw
660 Watts Max.
250 Volts
Height - 2¹/₈"




*** 22267**
Medium Base Socket
1/8"-IP Hickey
660 Watts Max.
250 Volts
Height - 2"
1875 Pulse Rated



*** 22269**
Keyless Socket
Medium Base
Bushing 1/8"-IP
With Set Screw
660 Watts Max.
250 Volts
Height - 2"



*** 22402**
**Socket
Adapter Reducer**
Reduces German or
Italian Base to
Candelabra Size
With Rubber Ring
75 Watts Max.
120 Volts



*** 22403**
**Socket
Adapter Reducer**
Reduces Intermediate Base
to Candelabra Base
With Rubber Ring
75 Watts Max.
120 Volts



*** 22406**
**Socket
Adapter Reducer**
Reduces Mogul Base
to Medium Base
660 Watts Max.
250 Volts



*** 22411**
**70361
Socket
Adapter Enlarger**
Enlarges Candelabra Base
to Medium Base
75 Watts Max.
120 Volt



*** 22471**
Mini Bi-Pin Quartz MR16 Socket
 GX5.3 Base
 12" 18 Gauge Leads
 SF-1 200° C Leads
 100 Watts Max., 250 Volts
 Height - 1"

*** 22470 - GY6.35 Base**
*** 22472 - GX5.3 Base**
Mini Bi-Pin Quartz MR16 Socket
 12" 18 Gauge Leads
 SF-1 200° C Leads
 100 Watts Max., 250 Volts
 Height - 3/8"

*** 22481**
High Pressure Sodium Lamp Socket
 9" Wire Leads
 Medium Base
 SF-2/SEW-2 200° Leads
 4 K.V. Pulse Rated
 660 Watts Max., 600 Volts
 1/2" Bushing
 Height - 1 1/4"

*** 22480**
High Pressure Sodium Lamp Socket
 9" Wire Leads
 Medium Base
 SF-2/SEW-2 200° Leads
 4 K.V. Pulse Rated
 660 Watts Max., 600 Volts
 1/2" Screw-Down
 Height - 1 1/4"




*** 11110**
Quartz Lamp Holder
 5" Wire Leads
 SF-1 200° C 300V Leads
 For 4 5/8" Lamp
 500 Watts Max.
 250 Volts
 Fits R7S, 4 5/8" Lamp Bases
 Height - 1 3/8"

*** 11112**
HQI Lamp Holder
 15" SF-2 200° C Leads
 1000 Watt Max.
 250 Volts
 For R7S Lamp Bases
 Height - 1 5/8"

*** 11109**
Quartz Lamp Holder
 5" Wire Leads
 SF-1 200° C
 500 Watts Max.
 250 Volts
 300 Volts Leads
 Fits R7S, 3 1/8" Lamp Bases
 Height - 1 5/8"

*** 11100**
Double Contact Bayonet Socket
 11" Wire Leads
 Threaded 1/8-IP
 SF-1 200° C 300V Leads
 150 Watts Max.
 125 Volts
 Height - 1 1/4"



*** 11104**
Porcelain Halogen Socket
 5" Wire Leads
 SF-1 200° C 300V Leads
 100 Watts Max., 250 Volts
 Fits G4, GX5.3, GV5.3
 and G6.35 Lamp Bases
 Height - 3/8"

*** 11107**
MR16 Porcelain Socket
 5" Wire Leads
 SF-1 200° C Leads
 75 Watts Max., 125 Volts
 Fits G5.3, GU5.3
 and GX5.3 Lamp Bases

*** 11108**
MR16 Porcelain Socket
 5" Wire Leads
 SF-1 200° C Leads
 75 Watts Max., 300 Volts
 Fits G5.3, GU5.3
 and GZ5.3 Lamp Bases

*** 11033**
Electronic Transformer
 Halogen
 Use with 12 Volt MR11 or MR16 Halogen Lamps
 Input 120 Volts AC
 Output 12 Volts, 80 Watt Max.
 3 1/2" White and 6" Black
 18 Gauge Leads

*Bulk Pack

CARDED PRODUCT SOLD IN INNER PACK ONLY

www.westinghouselighting.com



*** 22451**
Slimline Slide-On Lamp Holder
 Plunger Pedestal-Type
 Shallow End
 For T8 Lamps
 660 Watts Max., 1000 Volts



*** 22452**
Slimline Slide-On Lamp Holder
 Fixed Pedestal-Type
 Shallow End
 For T8 Lamps
 660 Watts Max., 1000 Volts



*** 22490**
Stationary End Lamp Holder
 For HO, VHO,
 SHO Lamps
 660 Watts Max., 1000 Volts



*** 22491**
Plunger End Lamp Holder
 For HO, VHO,
 SHO Lamps
 660 Watts Max., 1000 Volts



*** 22457**
Medium Bi-Pin Lamp Holder
Floating Action for U-Shape Lamps
 Low Profile Size
 20 Gauge
 660 Watts Max., 600 Volts



*** 22458**
Medium Bi-Pin Lamp Holder
Floating Action for U-Shape Lamps
 Low Profile Size
 Disconnect Feature Guards
 Against Electric Shock
 No. 18/20 Gauge
 660 Watts Max., 600 Volts



*** 22453**
Medium Bi-Pin Lamp Holder
 Low Profile Size
 660 Watts Max., 600 Volts
 T8/T12 Non Shunted



*** 22455**
Medium Bi-Pin Turn Type Lamp Holder
 Standard Size
 No. 20 Gauge
 Panel Mount
 660 Watts Max., 600 Volts



*** 22456**
Medium Bi-Pin Turn Type Lamp Holder
 Standard Size
 No. 18 Gauge
 Panel Mount
 660 Watts Max., 600 Volts



*** 22454**
Medium Bi-Pin Turn Type Lamp Holder
 Low Profile Size
 No. 18/20 Gauge
 Panel Mount, Captive
 Mount and Screw
 660 Watts Max., 600 Volts
 Non Shunted



Fluorescent Lamp Starters

- * 22560 - FS-2 - RoHS Compliant**
 14, 15 and 20 Watt Lamps
- * 22561 - FS-4**
 30 and 40 Watt Lamps
- * 22562 - FS-5 - RoHS Compliant**
 4, 6 and 8 Watt Lamps

Switches




*** 22324 - Nickel Finish
3-Way Canopy Switch With
4' White Braided Cord**
6" Wire Leads
18 Gauge, 105° Leads
Fits 3/8" Hole
1A, 125 VT
3A, 250 VAC
6A, 125 VL
6A, 125 VAC
Sequence of Operation:
Low / Medium / High / Off
Height - 1 3/16"




*** 22320 - Nickel Finish, 3' Cord
* 22321 - Brass Finish, 4' Cord
Pull Chain Canopy Switch
With White Braided Cord**
6" Wire Leads
18 Gauge, 105° Leads
Fits 3/8" Hole
3A, 250 VAC
6A, 125 VAC
6A, 125 VL
Height - 1 1/4"



*** 22303 - Brass Knob
Single Pole
Rotary Switch
Removable Knob**
6" Wire Leads
18 Gauge, 105° Leads
7/16" Nipple
Fits 3/8" Hole
1A, 125 VAC-L
1A, 250 VAC
3A, 120 VAC
Height - 1 1/16"



*** 22307
On/Off Push
Canopy Switch**
Brass Knob
6" Wire Leads
18 Gauge, 105° Lead
Fits 3/8" Hole
1A, 250 VAC
2A, 125 VT
3A, 120 VAC
Height - 1 1/8"



*** 22310
3-Way, 2 Circuit
Switch With
Removable
Brass Knob**
6" Wire Leads
18 Gauge, 105° Leads
3/8" Nipple
Fits 3/8" Hole
3A, 250 Volts
6A, 125 VT
Sequence of Operation:
1 On / 2 On / 1 & 2 On / Off
Height - 1 1/4"



*** 22306
Push Canopy
Switch**
4 3/4" Wire Leads
18 Gauge, 105° Leads
Fits 3/8" Hole
3A, 250 VAC
6A, 125 VL
6A, 125 VAC
Height - 1 1/4"

*Bulk Pack

CARDED PRODUCT SOLD IN INNER PACK ONLY

www.westinghouselighting.com



77022
Fan Light Switch
 With Chrome Finish
 Pull Chain, 2' Braided Cord
 3A, 250 VAC
 6A, 125 VAC



77023
Fan Light Switch
 With Polished Brass
 Pull Chain, 2' Braided Cord
 3A, 250 VAC
 6A, 125 VAC



77287
Fan Light Switch
 With Antique Brass
 Pull Chain, 2' Braided Cord
 3A, 250 VAC
 6A, 125 VAC




70290
Replacement Canopy Light Switch
 With Brass Pull Chain
 2' Braided Cord
 6" Wire Leads
 Height - 1 1/4"
 Fits 3/8" Hole



77285 - 3-Wire Unit
3-Way Fan Light Switch
 With Antique Brass
 Pull Chain, 2' Braided Cord
 3A, 250 VAC
 6A, 125 VAC



77052 - 3-Wire Unit
3-Way Fan Light Switch
 With Polished Brass
 Pull Chain, 2' Braided Cord
 3A, 250 VAC
 6A, 125 VAC



77091
Fan Capacitor
 3 MFD and 6.5 MFD
 3-Wire 150V



77288 - Dual Capacitor, 3-Wire Unit
3-Speed Fan Switch
 With Antique Brass
 Pull Chain, 2' Braided Cord
 3A, 250 VAC
 6A, 125 VAC



77286 - Single Capacitor, 4-Wire Unit
3-Speed Fan Switch
 With Antique Brass
 Pull Chain, 2' Braided Cord
 3A, 250 VAC
 6A, 125 VAC



77075 - Triple Capacitor, 8-Wire Unit
3-Speed Fan Switch
 With Polished Brass
 Pull Chain, 2' Braided Cord
 3A, 250 VAC
 6A, 125 VAC




77021 - Single Capacitor, 4-Wire Unit
3-Speed Fan Switch
 With Polished Brass
 Pull Chain, 2' Braided Cord
 3A, 250 VAC
 6A, 125 VAC

Crossbars

All crossbars are made of steel.


**Quick Assist Crossbar™
Patented Technology**



- U-slot design allows for easy adjustments without rewiring.
- Pre-assemble fixture before installation.
- No threading required so wires never twist during assembly.



70115 - Slips 1/8-IP
70116 - Slips 1/4-IP
Quick Assist Crossbar™
 45 lb. Load Rating
 Patent # 6,824,298
 Patent # 6,824,298



70112
4" Offset Crossbar
 Two 1/2" Mounting Screws
 and Two Tapped 5/32" Holes
 Spaced 2 3/4" Apart
 Slips 3/8-IP
 35 lb. Load Rating



* **21032**
70111
Adjustable
All-Purpose Crossbar
 Slips 3/8-IP
 Holes Tapped 8-32
 Adjusts from 3 7/8" to 5"
 for Slot Mounting on 3",
 3 1/4" or 4" Box
 Two 1/2" Head Screws Included
 Two 1/4" Head Screws Included
 35 lb. Load Rating



* **21003**
70113
4" Long Crossbar
 Tapped 1/8-IP
 45 lb. Load Rating



70110
4" Crossbar Kit
 Tapped 1/4-IP
 35 lb. Load Rating
 Includes:
 • 1 Crossbar
 • 1 3/8-IP x 1/4-IP Reducing Hickey
 • 1 1/4-IP x 1/8-IP Reducing Bushing
 • 2 8-32 x 1/2" Mounting Screws



70350 - Brass Finish
70352 - Antique Brass Finish
Screw Collar Loop Kit
 Fits Canopies with a 1 1/8" Center Hole
 Tapped 1/4-IP
 35 lb. Load Rating
 Includes:
 • 1 Crossbar
 • 1 Screw Collar Loop
 • 2 Locknuts
 • 1 Lock Washer
 • 1 1/4-IP x 1 1/2" Nipple
 • 1 3/8-IP x 1/4-IP Reducing Hickey
 • 2 x 1/2" Mounting Screws

*Bulk Pack

CARDED PRODUCT SOLD IN INNER PACK ONLY

www.westinghouselighting.com

All crossbars are made of steel.




*** 21038**
Circular Crossbar
 4 Holes Tapped 8-32
 2³/₄" Center to Center
 3¹/₂" Center to Center
 45 lb. Load Rating



*** 21031**
Universal Crossbar
 6 Holes Tapped 8-32
 1¹/₂" Center Hole 3⁷/₈"
 2¹/₈" Center to Center
 2³/₄" Center to Center
 3³/₈" Center to Center
 Green Ground Screw
 35 lb. Load Rating



*** 21006**
70114
Offset Crossbar
 4" Long
 8-32 Tapped Holes
 Green Ground Screw
 35 lb. Load Rating



*** 21030**
Universal Crossbar
 Slips ⁵/₈-IP
 Can Be Used for Porch Bracket,
 Ceiling Fixture or Any Other Type of
 Wall Mounted Lamp
 Easily Adjustable for Slot Mounting
 Two No. 10 Wood Screw Holes
 Will Adjust on 3", 3¹/₄" or 4" Box
 35 lb. Load Rating



*** 21008**
Crossbar
 3⁷/₈" Long
 Ground Screw Inserted
 Tapped ¹/₄-IP
 45 lb. Load Rating



*** 21004**
Crossbar
 4" Long
 Tapped ¹/₈-IP
 Green Ground Screw
 45 lb. Load Rating



*** 21005**
Crossbar
 4" Long
 Tapped ¹/₄-IP
 45 lb. Load Rating



*** 21036**
Crossbar Extension End
 Tapped 8-32
 Makes any crossbar adjustable.
 The combined load rating is a maximum of 30 lbs.
 when used in conjunction with another crossbar.

Nipples & All Thread

THREAD SIZES

Thread sizes come in several different types:

- 1/4-27 is 1/4" in diameter and fits harps and most finials
- 1/8-IP is 3/8" in diameter and fits ordinary lamp sockets
- 1/4-IP is 1/2" in diameter and is used in floor lamps



70151
Six Assorted Nipples

Zinc-Plated

- Includes:
- 2 1/4-IP x 3/4"
 - 2 1/4-IP x 1 1/2"
 - 2 1/4-IP x 2"



70150
Eight Assorted Nipples

Zinc-Plated

- Includes:
- 2 1/8-IP x 1/2"
 - 2 1/8-IP x 1"
 - 2 1/8-IP x 1 1/2"
 - 2 1/8-IP x 2"

1/4-27



1/8-IP



1/4-IP



3/8-IP



* **13352**
Brass Hex Head Nipple
Threaded 1/8-IP
Thread 3/16" Long

Steel Nipples Zinc-Plated

- * **13416** - 2" Long
- * **13418** - 3" Long
- * **13420** - 4" Long
- * **13424** - 6" Long
- 70613** - 6" Long (*Carded 2-Pack*)
Threaded 1/4-IP



Steel Nipples Zinc-Plated

- * **13204** - 1/2" Long
- * **13206** - 3/4" Long
- 70176** - 1" Long (*Carded 4-Pack*)
- * **13212** - 1 1/2" Long
- 70601** - 1 1/2" Long (*Carded 4-Pack*)
- * **13216** - 2" Long
- 70602** - 2" Long (*Carded 2-Pack*)
- * **13224** - 3" Long
- 70603** - 3" Long (*Carded 2-Pack*)
- * **13228** - 3 1/2" Long
- * **13232** - 4" Long
- 70604** - 4" Long (*Carded 2-Pack*)
- * **13248** - 6" Long
- 70606** - 6" Long (*Carded 2-Pack*)
Threaded 1/8-IP



* **13312** - 1 1/2" Long
Brass Running Thread Nipples
Threaded 1/8-IP


* **13650**
70270
30" Steel Brass-Plated All-Thread Pipe
Threaded 1/8-IP

* **13648**
Steel All-Thread Pipe
1/8-IP x 36"



70272
12" All-Thread Lamp Pipe Kit
Zinc-Plated Steel

- Includes:
- 2 1/8-IP x 12" Threaded Pipe
 - 2 1/8-IP Couplings
 - 2 1/8-IP Locknuts
 - 2 1/8-IP Knurled Locknuts
 - 2 Washers



*Bulk Pack

CARDED PRODUCT SOLD IN INNER PACK ONLY

www.westinghouselighting.com

Assorted Hardware




*** 12060 - Steel Hexagon**
Tapped 1/4-IP
Diameter - 1/16"



*** 12055 - Steel Hexagon**
Tapped 1/8-IP
Diameter - 3/16"



*** 11744 Hexagon**
Brass
Tapped 1/8-IP
Diameter - 1/2"




70620 Four Knurled Locknuts
Solid Brass
Tapped 1/8-IP




70155 Twelve Assorted Washers
Brass-Plated Steel
For 1/8-IP Nipples
Includes:
• 4 Lock Washers
• 4 Flat Washers
• 4 Rubber Washers




70628 Six Assorted Nuts and Washers
Brass-Plated Steel
For 1/8-IP Nipples
Includes:
• 2 Lock Washers
• 2 Flat Washers
• 2 Hex Nuts



**70621 - Solid Brass
70622 - Steel
Six Hex Nuts**
Tapped 1/8-IP



70172 Twelve Hex Nuts
Solid Brass
Tapped 1/8-IP



70152 Sixteen Assorted Hex Nuts
Steel
Includes:
• 4 8-32 Hex Nuts
• 2 1/4-27 Hex Nuts
• 6 1/8-IP Hex Nuts
• 2 1/4-IP Hex Nuts
• 2 3/8-IP Hex Nuts



70153 Twelve Assorted Locknuts
Solid Brass
Includes:
• 2 8-32 Battery Nuts
• 2 1/4-27 Threaded Knurled Locknuts
• 2 1/8-IP Knurled Locknuts
• 4 1/8-IP Hex Nuts
• 2 1/4-IP Knurled Locknuts



*** 10512 Plain Coupling**
Brass
Tapped 1/8-IP
3/16" Long



*** 10509 - Brass
70162 - Polished Brass (Carded 2 Pack)
Coupling**
Tapped 1/8-IP



*** 12224 Washer**
Brass-Plated
Slips 1/8-IP
Diameter - 1"



77016
20 - 1/2" Screws

Assorted for Fan Lights and Fan Blades

Includes:

- 5 - 8-32 Antique Brass Knurled Head Screws
- 5 - 8-32 Polished Brass Knurled Head Screws
- 5 - 10-24 Antique Brass Knurled Head Screws
- 5 - 10-24 Polished Brass Knurled Head Screws



70156
Thirteen Assorted Screws

Includes:

- 3 8-32 x 1/2" Brass-Plated
- 3 8-32 x 1/2" Nickel-Plated
- 3 8-32 x 3/4" Brass-Plated
- 2 8-32 x 1" Brass-Plated
- 2 8-32 x 2" Brass-Plated



70635
Fourteen Piece Metric Lighting Fixture Repair Kit

Includes:

- 2 - M4 x 10mm Philips Head Screws
- 2 - M4 x 12mm Knurled Head Screws
- 2 - M4 x 15mm Philips Head Screws
- 2 - M4 x 15mm Knurled Head Screws
- 2 - M4 x 25mm Cross Bar Screws
- 4 - M4 Knurled Knobs



70636
Five Round Head Screws

Brass-Plated Steel
8-32 Thread x 2" Long



77047 - Polished Brass Finish
77048 - Antique Brass Finish
10 Piece Motor Screw Kit

For Mounting Fan Blade Arms to Motor Housing



77040 - Polished Brass Finish
77041 - Antique Brass Finish
12 Fitter Screws

For Fan Lights



70660
Four Cap Nuts

Solid Brass
Diameter - 3/8"
Tapped 8-32



70632 - Brass-Plated Steel - 1/2" Long

70633 - Nickel-Plated Steel - 1/2" Long

70634 - Brass-Plated Steel - 3/4" Long
Three Knurled Head Screws

8-32 Thread



70254
1 3/8" Diameter Female Loop

Antique Brass Finish
Tapped 1/8-IP
40 lb. Load Rating



70258
Two 1" Diameter Female Loops

Brushed Nickel Finish
Tapped 1/8-IP
45 lb. Load Rating



70255
Two 1" Diameter Female Loops

Brass Finish
Tapped 1/8-IP
45 lb. Load Rating



70256
Two 1" Diameter Female Loops

Antique Brass Finish
Tapped 1/8-IP
45 lb. Load Rating



70250
Two 1" Diameter Female and Male Loops

Brass Finish
1/8-IP Thread
45 lb. Load Rating



*** 21530**
15" Diameter Female Loop

Brass-Plated and Lacquered
Tapped 1/8-IP
45 lb. Load Rating
Hole for Wiring
Diameter - 1 5/16" Height - 1 1/4"



70169 - Brass Finish
70640 - Nickel Finish
Two Lock-Up Caps

Diameter - 9/16"
Tapped 1/8-IP



70159 - Brass Finish
Two Lock-Up Caps

Diameter - 1"
Tapped 1/8-IP



70158 - White Finish
Two Lock-Up Caps

Diameter - 1 1/16"
Tapped 1/8-IP



70638 - Brass Finish
70639 - Nickel Finish
Lock-Up Kits

For Ceiling Glass
Tapped 1/8-IP

*Bulk Pack

CARDED PRODUCT SOLD IN INNER PACK ONLY

www.westinghouselighting.com

Assorted Hardware



77046 - White Six Beaded Chain Connectors



77045 - Chrome Six Beaded Chain Connectors



*** 16572 - Brass Beaded Chain Connector**



77044 - Solid Brass Six Beaded Chain Connectors



77066 - Antique Brass Six Beaded Chain Connectors



*** 16576 Brass Finish End Bell**
For Beaded Chain or Pull Cord

70661 Walnut Wooden Ball Pull Chain
36" Polished Brass Beaded Chain



Beaded Chain
.011 Gauge 1/8" Diameter Ball 75 Balls per Foot

Item No.	Length	Finish
* 16565	Sold by Foot or 250' Spool	Nickel
* 16564	Sold by Foot or 250' Spool	Brass


70662 * 16584 3' White Braided Cord
Nickel Finish Connector and End Bell Attached



Beaded Chain with Connector

.011 Gauge 1/8" Diameter Ball 75 Balls per Foot

Item No.	Length	Finish
70168	5 Ft.	Brass
77012	1 Ft.	Solid Brass
77050	3 Ft.	Solid Brass
77043	12 Ft.	Solid Brass
77064	3 Ft.	Antique Brass
77109	12 Ft.	Antique Brass
77051	3 Ft.	White Plastic
77054	3 Ft.	Oil Rubbed Bronze
77049	3 Ft.	Stainless Steel
77238	3 Ft.	Brushed Nickel
77063	3 Ft.	Chrome
77107	12 Ft.	Chrome




70168



77012
77050
77043

77049
77238
77063
77107



77051



77054



77064
77109

Canopies

* 61272

Traditional Canopy Kit

*Antique Brass Finish
7/16" Center Hole
50 lb. Load Rating
2 Holes Spaced 2 3/4" Apart*

- Includes:
- 1 Canopy
 - 1 Crossbar
 - 1 Lock Washer
 - 1 Locknut
 - 4 Mounting Screws
 - 1 Screw Collar Loop
 - 2 Cap Nuts
 - Polybagged



Traditional Canopy Kits with Center Hole

*5" Diameter
7/16" Center Hole
50 lb. Load Rating*

- Includes:
- 1 Canopy
 - 1 Crossbar
 - 4 Mounting Screws
 - 1 Lock Washer
 - 1 Locknut
 - 1 Screw Collar Loop
 - 2 Cap Nuts



70050
Oil Rubbed Bronze Finish



70048
Brushed Nickel Finish



70052
Brass Finish

70057

Canopy Hanger Kit

*Brass Finish
1 1/16" Center Hole
35 lb. Load Rating*

- Includes:
- 1 Canopy
 - 1 Crossbar
 - 1 Screw Collar Loop
 - 1 Hickey with Nipple
 - 2 Mounting Screws
 - 3 Locknuts



70053
Antique Brass Finish



70054
Brushed Pewter Finish



70055
Black Finish



70056
White Finish

* 18134

Canopy Extension Collar

*White Finish
Gives Canopy 1 1/2" Additional Depth
Depth - 1 1/2"
Diameter - 5 3/4"*



70045 Ceiling Blank-Up Kit

*White Finish
Diameter - 5"
7/16" Center Hole*

- Includes:
- 1 Canopy
 - 1 1/8-IP x 2 1/2" Nipple
 - 1 3/8-IP x 1/8-IP Reducing Bushing
 - 1 Cap Nut



70049 Canopy

*Antique Brass Finish
Diameter - 5"
1 1/16" Center Hole
(Use with Screw Collar Loop Kit, Item# 70352 on page 180)*

*Bulk Pack

CARDED PRODUCT SOLD IN INNER PACK ONLY

www.westinghouselighting.com

Modern Canopy Kits with Center Hole

5" Diameter

7/16" Center Hole

40 lb. Load Rating

Includes:

- 1 Canopy
- 1 Screw Collar Loop
- 2 Mounting Screws
- 1 Lock Washer
- 1 Locknut



70035
Modern Canopy Kit
Antique Brass Finish



70037
Modern Canopy Kit
White Finish



70033
Modern Canopy Kit
Brushed Nickel Finish



70059
Modern Canopy Kit
Brushed Pewter Finish



70036
Modern Canopy Kit
Black Finish



70038
Modern Canopy Kit
Oil Rubbed Bronze Finish



- * 29453 - Holes Spaced 2 3/4" Apart
 - * 70064 - Holes Spaced 2 3/4" Apart
 - * 29452 - Holes Spaced 3 1/2" Apart
 - * 70065 - Holes Spaced 3 1/2" Apart
- White Outlet Concealer**
 Diameter - 4 3/4"
 Mounts on 4" Outlet Box

Includes:

- 2 8-32 x 3/4" White Head Screws

**Bulk items are Polybagged*



70058
Blank-Up Kit
White Finish
 Diameter - 5"
 Holes Spaced 2 3/4" Apart

Includes:

- 1 Canopy
- 1 Crossbar
- 2 Mounting Screws
- 2 Cap Nuts

Swag Light Kits

Swag Kits Include:

- 11 Gauge Chain
 - SPT-1 Cord Set
 - Cord Switch
 - 2 Swag Hooks
 - Mounting Hardware
 - 35 lb. Load Rating
- Complete installation instructions included.*



**70483 - 12 Ft. Chain,
15 Ft. Cord**
Brushed Steel Finish
Clear Cord with White Switch
See Contents Listed on the left



**70470 - 15 Ft. Chain,
20 Ft. Cord**
**70480 - 12 Ft. Chain,
15 Ft. Cord**
Polished Brass Finish
*Gold Cord with
White Switch*



**70471 - 15 Ft. Chain,
20 Ft. Cord**
**70481 - 12 Ft. Chain,
15 Ft. Cord**
Antique Brass Finish
*Opaque Gold Cord with
Brown Switch*



**70530 - 15 Ft. Chain,
20 Ft. Cord**
**70531 - 12 Ft. Chain,
15 Ft. Cord**
White Finish
*White Cord with
White Switch*



**70486 - 12 Ft. Chain,
15 Ft. Cord**
Excavated Bronze Finish
Brown Cord with Brown Switch

Swag Kit Contents Listed Above



Swag Kits Include:

- 11 Gauge Chain
 - SPT-2 Cord Set
 - White Cord Switch
 - 2 Swag Hooks
 - Mounting Hardware
 - 35 lb. Load Rating
- Complete installation instructions included.*



**70126 - 18 Ft. Chain,
20 Ft. Cord**
Brushed Nickel Finish
See Contents Listed on the left



**77002 - 18 Ft. Chain,
20 Ft. Cord**
Antique Brass Finish



**70125 - 18 Ft. Chain,
20 Ft. Cord**
Oil Rubbed Bronze Finish



**77003 - 18 Ft. Chain,
20 Ft. Cord**
White Finish

Swag Kit Contents Listed Above

Swag Hooks & Chain



70446



70440



70441



70442



70443

Large 2½" Swag Hook Kits

- 70440 - Polished Brass Finish
- 70441 - Antique Brass Finish
- 70442 - Black Finish
- 70443 - White Finish
- 70446 - Brushed Pewter Finish

Hook Kits include:

- 1 Spring Toggle Wing
- 1 Running Thread Stud: ¼-20 x 2 7/8"
- 1 Wood Screw: #14 x 1 5/8"
- 45 lb. Load Rating



70444

70450

70451
*21241

70452

70453

70457

70770
*21249



70454

1½" Swag Hook Kits

- 70444 - Brushed Pewter Finish
- 70450 - Polished Brass Finish
- 70451 - Antique Brass Finish
- 70452 - Black Finish
- 70453 - Antique Copper Finish
- 70454 - Oil Rubbed Bronze Finish
- 70457 - Rust Finish
- 70770 - White Finish

- 21241 - Antique Brass Finish
- 21249 - White Finish

Hook Kits include:

- 2 Hooks
- 2 Spring Toggle Wings
- 2 Running Thread Studs: #10-24 x 2 7/8"
- 2 Wood Screws: #10 x 1 1/4"
- 30 lb. Load Rating



70062

70070

70071

70072

70074

70075

70079

70670

3 Ft. 11 Gauge Fixture Chains, 35 lb. Load Rating

- 70062 - Brushed Pewter Finish
- 70070 - Polished Brass Finish
- 70071 - Antique Brass Finish
- 70072 - Flat Black Finish
- 70074 - Oil Rubbed Bronze Finish
- 70075 - Brushed Nickel Finish
- 70079 - Rust Finish
- 70322 - Tiffany Antique Finish
- 70670 - White Finish

8 Gauge Fixture Chains, 50 lb. Load Rating, Sold by the Yard

- * 21461 - Chrome Finish
- * 21464 - Antique Brass Finish
- * 21457 - Flat Black Finish

70322

*Bulk Pack

www.westinghouselighting.com

CARDED PRODUCT SOLD IN INNER PACK ONLY

Make-A-Lamp Kits

70025 Electrified Candlestick and Bottle Adapter


Includes:

- 8' 18 Gauge Cord Set
- Push-Through Medium Base Socket
- 150 Watts Max. Rating
- 3 Rubber Bottle Adapters
- Hardware



* 69559 70099 Fixture Chain Pliers


7" Long
Used for Easy Opening
and Closing of Chain Links
Works with up to 3 Gauge Chain



70268 3-Way Socket Kit

Includes:


- 10" Brass-Plated Detachable Harp
- 8' 18 Gauge Cord Set
- 3-Way Medium Base Socket
- 150 Watts Max. Rating
- Finial
- Hardware



70269 Push-Through Socket Kit

Includes:

- 10" Brass-Plated Detachable Harp
- 8' 18 Gauge Cord Set
- Push-Through Medium Base Socket
- 150 Watts Max. Rating
- Finial
- Hardware



70266 Electric Bottle Adapter Kit

Includes:

- 10" Brass-Plated Detachable Harp
- 8' 18 Gauge Cord Set
- Push-Through Medium Base Socket
- 150 Watts Max. Rating
- Decorative Finial
- 3 Rubber Bottle Adapters
- Hardware

*Bulk Pack

CARDED PRODUCT SOLD IN INNER PACK ONLY

www.westinghouselighting.com

Harps



70551
Two Compact Fluorescent Lamp Harp Expanders

For use with Compact Fluorescent Lamps with Larger Ballasts

Brass Finish

Height - 7/8"

Width - 1 1/16"

Depth - 3/8"

* 19104 - 8"

* 19106 - 9"

* 19108 - 10"

Two-Piece Brass-Plated Heavy-Duty Detachable Harp



70218 - 6 1/2"

70220 - 8"

70221 - 9"

70222 - 10"

70224 - 12"

Two-Piece Polished Brass Finish Detachable Harp



70226 - 8"

70227 - 10"

70228 - 12"

Two-Piece Brushed Pewter Finish Detachable Harp



70689 - 8"

70690 - 10"

Two-Piece Rustic Bronze Finish Detachable Harp



* 19066 - 7"

* 19067 - 7 1/2"

* 19068 - 8"

* 19070 - 9"

* 19071 - 9 1/2"

* 19072 - 10"

* 19074 - 11"

Two-Piece Brass-Plated Detachable Harp



* **28151**
70219
Clip-On Lamp Adapter

Clips Onto Medium Base

A-Shape Lamps

Brass Finish

Threaded 1/4-27

Height - 3 1/16"

Width - 2 1/8"

Depth - 1/2"

Overall Height - 4"



70216
Clip-On Lamp Adapter

Clips onto Candelabra

Base Lamps

Brass Finish

Threaded 1/4-27

Height - 2 1/2"

Width - 1"

Depth - 7/8"

Overall Height - 3 1/8"

*Bulk Pack

www.westinghouselighting.com

CARDED PRODUCT SOLD IN INNER PACK ONLY

Finials, Knobs and Risers

70681
Ornate Lantern
Lamp Finial

Aged Iron Finish
 Height - 2 $\frac{7}{8}$ "
 Tapped $\frac{1}{4}$ -27



70320
Victorian
Lamp Finial

Tiffany Antique
Brass Finish
 Height - 3 $\frac{1}{2}$ "
 Tapped $\frac{1}{4}$ -27



70699
Baroque Scroll
Lamp Finial

Black Iron Finish
 Height - 2 $\frac{3}{4}$ "
 Tapped $\frac{1}{4}$ -27



70133
Acorn Knob
Lamp Finial

Brass Finish
 Height - 1 $\frac{1}{2}$ "
 Tapped $\frac{1}{4}$ -27
 Finial Thread Reducer
 Tapped $\frac{1}{8}$ -M to $\frac{1}{4}$ -27-F



70141
Acorn Knob
Lamp Finial

Nickel Finish
 Height - 1 $\frac{1}{2}$ "
 Tapped $\frac{1}{4}$ -27
 Finial Thread Reducer
 Tapped $\frac{1}{8}$ -M to $\frac{1}{4}$ -27-F



70321
Victorian
Lamp Finial

Tiffany Antique
Brass Finish
 Height - 1 $\frac{3}{8}$ "
 Tapped $\frac{1}{4}$ -27



70004
Semi Ornate Floral
Lamp Finial

Oil Rubbed
Bronze Finish
 Height - 1 $\frac{1}{2}$ "
 Tapped $\frac{1}{4}$ -27



70686
Clear Glass Ball
Lamp Finial

Brass Finish
 Height - 1 $\frac{7}{8}$ "
 Tapped $\frac{1}{4}$ -27



70005
Classic Ball
Lamp Finial

Oil Rubbed
Bronze Finish
 Height - 1 $\frac{1}{2}$ "
 Tapped $\frac{1}{4}$ -27



70006
Classic Ball
Lamp Finial

Brushed Nickel
Finish
 Height - 1 $\frac{1}{2}$ "
 Tapped $\frac{1}{4}$ -27



* 10706
70140 (Carded 2-Pack)
Shade Riser
 Solid Brass
 Height - 1"
 ¼-27 Thread
 Male and Female Threads



* 10708
Riser
 Solid Brass
 Height - 1⅞"
 ¼-27 Thread



* 10710
Riser
 Solid Brass
 Height - 2"
 ¼-27 Thread



70130 (Carded 2-Pack)
Two Lamp Finials
 Solid Brass
 Height - 2"
 Tapped ¼-27



70144 (Carded 2-Pack)
Two Lamp Finials
 Nickel Finish
 Height - 1"
 Tapped ¼-27



70131 (Carded 2-Pack)
Two Lamp Knobs
 Brass Finish
 Height - 1¼"
 Tapped ¼-27



70138 (Carded 2-Pack)
Two Lamp Knobs
 Nickel Finish
 Height - 1¼"
 Tapped ¼-27



70135
Lamp Finial
 Solid Brass
 Height - 2"
 Tapped ¼-27



70143
Lamp Finial
 Nickel Finish
 Height - 2"
 Tapped ¼-27



* 10649
70676
Lamp Finial
 Aged Iron Finish
 Height - 2"
 Tapped ¼-27



* 16355 - Height - ½"
 * 16356 - Height - 1"
70136 - Height - 1"
(Carded 2-Pack)
Lamp Finial
 Brass Finish
 Tapped ¼-27



* 10605
Finial
 Burnished and
 Lacquered
 Height - 1"
 Tapped ¼-27



* 11700
**Small Knurled
 Battery Nut**
 Brass
 Tapped ⅝



* 10600
Solid Brass Knob
 Polished Brass
 Tapped ¼-27



* 22367 - White
 * 22366 - Brown
Heavy-Duty On/Off Switch
 For Use with No. 18, SPT-2 Wire Only
 T-Rated
 3A, 125 Volts
 3A, 250 Volts
 6A, 125 Volts



* 22352
Cord Switch
 Black
 For Use with SPT-1 Wire
 T-Rated
 3A, 125 Volts
 3A, 250 Volts
 6A, 125 Volts



* 22357 - White
 * 22359 - Brown
On/Off Switch
 For Use with No. 18, SPT-1 Wire
 T-Rated
 3A, 125 Volts
 3A, 250 Volts
 6A, 125 Volts



* 22354
Feed-Through Cord Switch
 Brown
 Use with SPT-1 or SPT-2 Wire
 3A, 125 VAC
 1/2 HP, 125 VAC



70506 - Brown Finish
 70500 - White Finish
Feed-Through On/Off Switch
 For Use with No. 18, SPT-1 Wire Only
 3A



77270
48" Down Rod Wire Extension Kit
 4 Wires with 4 Connectors



* 21494
Slips 8/32 Thread
 Bare Copper Ground Wire With Lug
 9" Lead



70641
10' Copper Ground Wire
 18 Gauge



Cord Sets
 18/2 SPT-1, 105° Wire
Transparent Silver
 * 23055 - 15 Foot
Opaque Gold
 * 23034 - 8 Foot
Transparent Gold
 * 23033 - 8 Foot
 * 23053 - 15 Foot



Cord Sets
 18/2 SPT-1, 105° Wire
Black
 * 23032 - 8 Foot
 * 23052 - 15 Foot
White
 * 23020 - 6 Foot
 * 23030 - 8 Foot
 * 23050 - 15 Foot
Brown
 * 23031 - 8 Foot
 * 23051 - 15 Foot



70103
15' Gold Cord Set
 Polarized Plug
 18-2 SPT-1, 105° Wire



70098
8' Silver Cord Set
 Polarized Plug
 18-2 SPT-2, 105° Wire



70101 - SPT-1
 70107 - SPT-2
8' Brown Cord Set
 Polarized Plug
 18-2, 105° Wire



70100 - SPT-1
 70106 - SPT-2
8' White Cord Set
 Polarized Plug
 18-2, 105° Wire



70105 - SPT-1
 70102 - SPT-2
8' Gold Cord Set
 Polarized Plug
 18-2, 105° Wire


On All Cord Sets Free Ends are Split, Stripped and Tipped

*Bulk Pack

CARDER PRODUCT SOLD IN INNER PACK ONLY

www.westinghouselighting.com

Parts and Accessories




Great for Seasonal Ceramics and Crafts

- * 23305 - 6 Foot White
 - 70108 - 6 Foot White
 - * 23306 - 6 Foot Brown
 - 70003 - 6 Foot Brown
- Cord Set with Snap-In Pigtail Candelabra Base Socket and Cord Switch**
 No. 18-2, SPT-1, 105° Wire
 75 Watts, 125 Volts
 Snap-In Spring Fits 1" Hole
 Switch is 12" from Socket




- * 23300 - 6 Foot White
 - * 23302 - 8 Foot White
 - * 23303 - 8 Foot Brown
- Cord Set With Switches Cat Tipped**
 No. 18-2, SPT-1, 105° Wire
 Wire Switch is 12" from End



- * 23311 - 6 Foot White
- Cord Set With Snap-In Pigtail Candelabra Base Socket**
 No. 18-2, SPT-1, 105° Wire
 75 Watts
 125 Volts
 Fits 1" Hole
 Snap-In Spring Fits 1" Hole



- 70801**
Halogen Dimmer For Torchiere Lamps
 Includes Knob
 500 Watt Maximum, 120 VAC



*Bulk Pack
www.westinghouselighting.com

CARDER PRODUCT SOLD IN INNER PACK ONLY


Plugs




* 22600 - Brown
 * 22601 - Ivory
Easy Connect Plug
 Polarized
 SPT-1 Wire, Side Entry



* 22631 - Brown
 * 22632 - White
Polarized Automatic Plug
 SPT-1 Wire, Top Entry




* 22634
3-Prong Plug
 Steel Cord Clamp
 7/16" Hole
 15A, 125 Volts



* 22633
Heavy Duty Outdoor 3-Prong Plug
 Plastic Cord Clamp
 7/16" Hole
 15A, 125 Volts
 Cord Grip Range 245-700"
 12 thm, 18 AWG




* 22635
Heavy Duty Outdoor Female Connector
 Plastic Cord Clamp
 3/8" Hole
 15A, 125 Volts



74321 - Clear
Eight Safety Caps
 Covers Outlets



* 22532
Snap-In Outlet with Ground Wire
 Black
 6" Wire Leads
 14 Gauge
 15A, 125 Volts
 Fits 1" Square Opening
 with Green Ground Wire
 Height - 7/8"



* 22738
Vinyl Parallel Ground Adapter
 Polarized
 15A, 125 Volts

*Bulk Pack

CARDED PRODUCT SOLD IN INNER PACK ONLY

www.westinghouselighting.com

Accessories



- * 24105 - 3" Long
 - * 24109 - 4" Long
 - 70370 - 4" Long (Carded 2-Pack)
 - * 24115 - 6" Long
- White Plastic
Candle Socket Cover**
Candelabra Base
I.D. - $\frac{3}{4}$ "
O.D. - $\frac{7}{8}$ "



- * 24140 - 4" Long White
 - 70371 - 4" Long White (Carded 2-Pack)
 - 70374 - 4" Long Ivory (Carded 2-Pack)
 - * 24147 - 6" Long White
- White Plastic
Candle Socket Cover**
Medium Base
I.D. - $1\frac{3}{16}$ "
O.D. - $1\frac{1}{4}$ "



- * 24059
 - 70373 - (Carded 2-Pack)
- Ivory Plastic
Candle Socket Cover**
4" Long
Candelabra Base
I.D. - $\frac{3}{4}$ "
O.D. - $\frac{7}{8}$ "




- * 24050
- Brown Fiber Drip
Candle Socket Cover**
4" Long
Candelabra Base
I.D. - $\frac{3}{4}$ "
O.D. - $\frac{7}{8}$ "



- 70368
- Two 4" Plastic
Candle Socket Covers**
Tan Drip
Candelabra Base
I.D. - $\frac{3}{4}$ "
O.D. - $\frac{7}{8}$ "



- 70300
- Five $1\frac{1}{2}$ "
Crystal Prisms**
Clear




- 70312
- Five 3"
Crystal Prisms**
Clear



- 74998 - Single Gang
 - 74999 - Double Gang
- Plastic Wall Shield**



* 12082 - White
 * 12084 - Cream
3" x 4" x 4"
Pleated Shades
 Clips on to
 Torpedo Bulbs



* 28212
6" Diameter
Green Felt Pad
 Adhesive Backing

70900 - White Finish
40" Wire Cover
 Can be painted or stained
 Use latex stain only



* 41298 - 16 oz.
 * 41299 - 32 oz.
Extend-A-Finish
Crystal and Fixture
Cleaner

- Features:
- Will Not Streak or Spot
 - Drip Dry
 - No Ammonia
 - Will Not Harm Metal Framework or Finish



70298
Extend-A-Finish
Crystal and Fixture
Cleaner
 Convenient 6-pack bin
 box of 41298



7709908
Duster Display
 Contains 12 Dusters
 (Item# 77105)



77105
All Purpose
Electrostatic Duster

- Telescopic handle extends up to 72"
- Flexible head adjusts to any angle
- Perfect for cleaning fan blades, fixtures or any other hard-to-reach household items



Can Adjust to Any Angle

*Bulk Pack

CARDED PRODUCT SOLD IN INNER PACK ONLY

www.westinghouselighting.com

Item#	Page#	Item#	Page#	Item#	Page#	Item#	Page#
01010	139	13206	182	22031	171	22371	173
• 01010DISP	139	13212	182	22033	171	22372	174
• 01011	7, 43, 135	13216	182	22041	171	22377	170
01020	143	13224	182	22051	171	22380	170
• 01020DISP	143	13228	182	22053	171	22381	170
0102011	143	13232	182	22125	172	22382	170
01030	145	13248	182	22126	172	22402	175
0103011	145	13312	182	22127	172	22403	175
01036	145	13352	182	22135	172	22406	175
• 01036DISP	145	13416	182	22136	172	22411	175
0103611	145	13418	182	22138	172	22451	177
0104011	143	13420	182	22150	174	22452	177
01050	143	13424	182	22200	170	22453	177
• 01050DISP	143	13648	182	22203	170	22454	177
0105011	143	13650	182	22205	169	22455	177
0105211	143	16074	175	22207	169	22456	177
01070	147	16355	193	22212	173	22457	177
01100	140	16356	193	22213	170	22458	177
• 01100DISP	140	16564	132, 185	22214	170	22470	176
01240	144	16565	132, 185	22215	170	22471	176
• 01240DISP	144	16572	132, 185	22216	170	22472	176
0124011	144	16576	132, 185	22217	170	22480	176
01250	144	16584	185	22218	174	22481	176
0125011	144	18134	186	22220	170	22490	177
01400	141	19066	191	22221	170	22491	177
01525	142	19067	191	22222	170	22501	169
• 01525DISP	142	19068	191	22223	170	22502	169
0152511	142	19070	191	22234	169	22503	169
0200011	146	19071	191	22237	169	22504	169
0252511	146	19072	191	22256	168	22505	169
• 02525DISP	146	19074	191	22259	168	22517	171
10509	183	19104	191	22264	174	22532	196
10512	183	19106	191	22266	174	22551	171
10600	193	19108	191	22267	175	22560	177
10605	193	21003	180	22269	175	22561	177
10649	193	21004	181	22272	173	22562	177
10706	193	21005	181	22273	174	22600	196
10708	193	21006	181	22274	175	22601	196
10710	193	21008	181	22276	174	22631	196
11033	176	21030	181	22281	174	22632	196
11100	176	21031	181	22282	174	22633	196
11104	176	21032	180	22303	178	22634	196
11107	176	21036	181	22306	178	22635	196
11108	176	21038	181	22307	178	22738	196
11109	176	21241	189	22310	178	22745	168
11110	176	21249	189	22320	178	23020	194
11112	176	21457	189	22321	178	23030	194
11700	193	21461	189	22324	178	23031	194
11744	183	21464	189	22352	194	23032	194
12055	183	21494	194	22354	194	23033	194
12060	183	21530	184	22357	194	23034	194
12082	198	22001	171	22359	194	23050	194
12084	198	22003	171	22366	194	23051	194
12224	183	22011	171	22367	194	23052	194
13204	182	22013	171	22370	132, 173	23053	194

• *New Item*

Item#	Page#	Item#	Page#	Item#	Page#	Item#	Page#
23055	194	62240	27, 36	63013	7	66088	42
23300	195	62244	27, 49	• 63018	8	66098	42
23302	195	62245	27, 63	• 64000	74	66161	53
23303	195	62247	27, 63	• 64001	74	66162	53
23305	195	62252	26, 39	• 64002	74	66176	53
23306	195	62254	29, 39	• 64003	74	66177	50
23311	195	62255	29, 39	• 64004	74	66198	42
24050	197	62256	29, 45	64290	49	66200	60
24059	197	62257	28, 47	64291	49	66201	60
24105	197	62258	28, 47	64292	49	66203	59
24109	197	62259	28, 47	64300	53	66204	59
24115	197	62260	28, 65	64301	53	66205	60
24140	197	62261	28, 65	64302	53	66206	60
24147	197	62262	28, 65	64303	53	66214	59
28151	191	62264	30, 38	64304	52	66220	20, 63
28212	198	62265	30, 38	64305	52	66223	20, 49
29452	187	62266	30, 43	64306	52	66233	78
29453	187	62267	30, 67	64308	48	66238	59
41298	198	62268	23, 38	64309	51	66239	59
41299	198	62269	23, 38	64311	50	66240	59
61272	186	62270	23, 47	64316	51	66241	59
62200	20, 36	62271	23, 47	64321	55	66242	60
62201	20, 44	62272	23, 67	64323	54	66244	42
62203	20, 49	62273	23, 67	64340	55	66253	48
62204	20, 63	62274	19, 39	64358	55	66254	50
62205	20, 63	62275	19, 39	64360	55	66263	60
62206	33, 37	62276	19, 47	64361	54	66282	54
62207	33, 37	62278	19, 66	64363	52	66295	36
62208	33, 43	62279	19, 66	64516	82	66296	43
62209	33, 44	62280	22, 38	64532	45	66297	60
62210	33, 50	62281	22, 38	64615	34, 41	66323	54
62211	33, 50	62282	22, 47	64617	70	66326	61
62212	33, 63	62284	22, 67	64681	81	66327	53
62213	33, 63	62285	22, 67	64683	77	66329	56
62214	25, 36	62286	30, 41	64684	81	66339	55
62215	25, 36	62287	30, 47	64686	83	66378	53
62217	25, 44	62288	30, 67	64687	83	66401	71
62219	25, 49	62301	75	64688	82	66402	71
62220	25, 65	62302	76	64689	82	66403	71
62221	25, 65	62303	76	64829	80	66405	71
62222	25, 65	62306	78	64830	80	66406	72
62223	21, 37	62307	76	64841	75	66410	71
62224	21, 37	• 62308	76	64864	75	66411	72
62225	21, 48	• 62309	76	64865	75	66414	72
62227	21, 64	• 62311	21, 66	64866	75	66424	71
62229	24, 37	• 62312	21, 66	64883	81	66442	72
62230	24, 37	63000	9	65302	60	66443	72
62231	24, 48	63002	9	65659	124	66448	72
62233	24, 64	63003	9	65661	124	66449	72
62234	24, 64	63005	9	65680	124	66450	72
62235	34, 41	63006	8	65682	124	66464	54
62236	34, 48	63008	8	66008	34, 41	66465	54
62237	34, 48	63009	9	66028	21, 48	66468	55
62238	34, 64	63011	9	66031	21, 64	66490	69
62239	34, 64	63012	7	66054	40	66491	69

• *New Item*

Item#	Page#	Item#	Page#	Item#	Page#	Item#	Page#
66492	69	66828	79	67331	66	69395	78
66494	69	66832	77	67345	59	69407	76
66495	69	66839	86	67384	45	69449	51
66496	70	66840	85	67477	68	69450	51
66497	70	66853	77	•67480	8	69559	190
66499	69	66859	87	•67481	8	69610	81
66521	68	66860	87	•67482	8	69823	77
66522	68	66861	85	•67485	8	69919	80
66523	68	66875	87	67492	78	70001	175
66584	32, 40	66878	86	67509	78	70003	195
66587	32, 40	66879	84	67512	68	70004	192
66590	32, 44	66881	84	67513	68	70005	192
66592	32, 65	66884	86	67514	68	70006	192
66593	32, 65	66885	86	67515	68	70010	173
66594	72	66898	80	67518	80	70025	190
66595	72	66919	86	67519	78	70029	126
66596	32, 63	66924	77	67533	69	70030	126
66599	32, 48	66935	81	67543	75	70031	126
66600	58	66936	81	67545	75	70032	126
66601	71	66937	81	67572	52	70033	187
66603	58	66938	81	67573	52	70035	187
66604	57	66945	85	67605	54	70036	187
66607	58	66946	87	67831	79	70037	187
66609	56	66949	86	67834	79	70038	187
66610	56	66955	84	67835	84	70042	168
66611	57	66961	82	67836	84	70045	186
66624	61	66962	82	67843	79	70048	186
66640	31, 41	66963	83	67846	79	70049	186
66645	31, 52	66964	83	67847	79	70050	186
66646	31, 52	66970	77	67850	79	70052	186
66647	31, 67	66971	81	67851	79	70053	186
66649	31, 67	66972	81	67863	77	70054	186
66654	71	66975	87	67864	77	70055	186
66658	58	66976	87	67873	77	70056	186
66662	70	66983	83	67887	83	70057	186
66677	58	66984	83	67899	66	70058	187
66678	57	66991	84	67901	84	70059	187
66680	58	67015	65	67904	78	70062	189
66681	57	67017	45	67905	78	70064	187
66686	61	67141	40	67930	80	70065	187
66689	56	67142	51	67963	82	70070	189
66692	58	67143	42	67973	84	70071	189
66698	56	67202	56	67975	84	70072	189
66699	57	67208	58	67978	85	70074	189
66741	76	67209	56	67980	85	70075	189
66742	76	67210	56	69000	26, 40	70079	189
66746	76	67212	56	69001	26, 40	70098	194
66748	80	67215	57	69006	26, 44	70099	190
66800	86	67225	51	69009	26, 64	70100	194
66803	85	67226	70	69192	50	70101	194
66808	84	67241	50	69193	50	70102	194
66818	86	67314	55	69222	41	70103	194
66822	87	67322	61	69231	45	70105	194
66823	87	67325	61	69234	70	70106	194
66826	79	67328	80	69246	51	70107	194

• *New Item*

Item#	Page#	Item#	Page#	Item#	Page#	Item#	Page#
70108	195	70242	168	70430	169	70699	192
70110	180	70243	168	70431	171	70770	189
70111	180	70244	168	70433	169	70801	195
70112	180	70250	184	70435	175	70900	198
70113	180	70254	184	70440	189	72141	99
70114	181	70255	184	70441	189	72161	99
70115	180	70256	184	70442	189	•72229	94
70116	180	70258	184	70443	189	72243	94
70125	188	70266	190	70444	189	72245	95
70126	188	70268	190	70446	189	72261	96
70130	193	70269	190	70450	189	7226565	102
70131	193	70270	182	70451	189	72280	116
70133	192	70272	182	70452	189	7234265	102
70135	193	70284	7	70453	189	72345	116
70136	193	70285	7	70454	189	72470	105
70138	193	70286	7	70457	189	72471	94
70140	193	70287	7	70470	188	72472	95
70141	192	70290	179	70471	188	72473	97
70143	193	70298	198	70480	188	72474	98
70144	193	70300	197	70481	188	72475	95
70145	169	70312	197	70483	188	72476	105
70146	169	70320	192	70486	188	72477	101
70150	182	70321	192	70500	194	72478	116
70151	182	70322	189	70506	194	72557	93
70152	183	70350	180	70530	188	72559	102
70153	183	70352	180	70531	188	72598	97
70155	183	70361	175	70551	191	74321	196
70156	184	70364	174	70601	182	74998	197
70158	184	70368	197	70602	182	74999	197
70159	184	70370	197	70603	182	75050	89
70160	171	70371	197	70604	182	75051	89
70161	171	70373	197	70606	182	75052	89
70162	183	70374	197	70613	182	75053	89
70168	132, 185	70402	172	70620	183	77002	188
70169	184	70403	172	70621	183	77003	188
70172	183	70404	172	70622	183	77004	129
70176	182	70405	172	70628	183	77005	129
70216	191	70407	169	70632	184	77006	130
70218	191	70408	173	70633	184	77007	128
70219	191	70409	173	70634	184	77008	128
70220	191	70410	171	70635	184	77009	128
70221	191	70411	171	70636	184	77010	130
70222	191	70412	171	70638	184	77011	130
70224	191	70413	171	70639	184	77012	132, 185
70226	191	70414	168	70640	184	77013	128
70227	191	70417	171	70641	194	77014	128
70228	191	70419	173	70660	184	77015	132
70229	168	70420	173	70661	128, 185	77016	132, 184
70230	168	70421	171	70662	185	77019	128
70231	168	70423	174	70670	189	77021	133, 179
70234	168	70424	173	70676	193	77022	133, 179
70236	168	70425	173	70681	192	77023	133, 179
70238	168	70426	173	70686	192	77027	138
70240	168	70428	175	70689	191	77028	138
70241	168	70429	173	70690	191	77029	128

• *New Item*

Item#	Page#	Item#	Page#	Item#	Page#	Item#	Page#
77030	128	77214	129	77630	127	7824865	96
77034	138	77215	129	77635	127	7826765	108
77035	138	77217	129	77638	130	78377	109
77036	128	77218	129	77640	127	7839165	107
77037	138	77220	128	77642	127	78399	104
77040	132, 184	77224	128	77644	130	78400	104
77041	132, 184	77225	128	77645	130	78409	118
77043	132, 185	77238	132, 185	77732	138	7843565	108
77044	132, 185	77240	124	77733	138	78505	101
77045	132, 185	77241	124	77750	137	78507	101
77046	132, 185	77242	124	77752	137	78508	109
77047	132, 184	77243	124	77754	137	78509	109
77048	132, 184	77244	124	77756	137	78510	109
77049	132, 185	77245	124	77757	137	7852165	106
77050	132, 185	77246	124	77762	137	78524	99
77051	132, 185	77249	124	77764	137	7856865	106
77052	133, 179	77251	124	77811	123	78603	112
77054	132, 185	77252	124	77812	123	78614	118
77058	132	77254	124	77813	123	78615	109
77059	132	77255	124	77814	123	78616	111
77060	131	77257	124	77815	123	7861965	115
77061	131	77265	124	77823	123	7862765	107
77063	132, 185	77268	131	77826	123	78631	94
77064	132, 185	77269	132	77832	123	•78644	94
77066	132, 185	77270	133, 194	77838	123	78660	110
77069	128	77285	133, 179	77840	125	7867865	107
77072	128	77286	133, 179	77870	125	78691	98
77074	131	77287	133, 179	77872	125	78714	110
77075	133, 179	77288	133, 179	77873	125	78715	111
77076	131	77289	130	77874	125	78716	110
77077	132, 173	77290	128	77875	125	78763	95
77079	131	77291	128	77934	124	78764	97
77083	128	77292	128	77935	124	•7877365	108
77084	130	77293	130	•78000	114	78775	98
77087	128	77294	127	•78001	93	7877865	115
77088	130	77400	131	•78002	93	7877965	115
77091	133, 179	77401	131	•78003	119	7879965	105
77093	130	77402	131	•78004	111	81051	15, 154
77095	129	77405	131	•78005	112	81066	155
77096	129	77406	131	7801665	100	81067	154
77097	129	77407	131	7801765	100	81072	15, 154
7709908	131, 198	77410	131	78024	119	81082	155
77103	129	77411	131	7804365	107	81094	155
77104	129	77414	131	78053	112	81095	15, 154
77105	131, 198	77415	131	7807765	106	81096	155
77107	132, 185	77416	131	7807965	106	81097	15, 154
77108	129	77491	124	78108	112	81098	13, 152
77109	132, 185	77492	124	78123	113	81099	15, 154
77118	127	77526	124	78125	113	81100	164
77121	129	77527	124	78126	113	81104	164
77122	127	77528	124	78127	118	81112	158
77123	127	77620	127	7813365	113	81119	13, 152
77125	127	77621	127	7813665	100	81120	14, 153
77127	130	77626	130	7814465	96	81121	13, 152
77134	130	77628	127	7814565	96	81135	14, 153

•New Item

www.westinghouselighting.com

Item#	Page#	Item#	Page#	Item#	Page#	Item#	Page#
81151	164	81457	163	81901	162	85869	162
81160	158	81459	163	81902	162	85888	162
81162	158	81479	155	81905	162		
81167	13, 152	81493	165	81918	162		
81169	158	81494	165	81919	162		
81170	158	81499	165	81920	163		
81208	151	81501	161	81925	156		
81227	15, 154	81504	161	83062	158		
81230	164	81514	165	83063	158		
81242	155	81528	157	83070	159		
81253	15, 154	81549	160	83071	159		
81254	160	81558	160	83072	158		
81257	13, 152	81560	161	83073	158		
81258	155	81570	161	83090	159		
81265	13, 152	81571	161	83091	159		
81270	15, 154	81574	161	83100	159		
81272	13, 152	81575	161	83101	159		
81275	151	81578	157	83102	159		
81277	15, 154	81590	164	83103	159		
81279	13, 152	81592	157	83112	159		
81282	155	81602	160	83131	159		
81290	157	81604	164	83757	157		
81303	12, 151	81606	157	85100	164		
81310	11, 150	81609	157	85151	164		
81311	11, 150	81613	157	85162	158		
81314	12, 151	81617	164	85254	160		
81315	12, 151	81620	157	85338	160		
81333	14, 153	• 81631	10, 149	85450	162		
81338	160	81707	161	85451	163		
81353	14, 153	81712	160	85528	157		
81355	153	81720	156	85570	161		
81356	13, 152	81727	156	85571	161		
81363	13, 152	81750	156	85578	157		
81364	12, 151	81758	164	85602	160		
81365	14, 153	81759	164	85604	164		
81375	14, 153	81760	164	85606	157		
81382	14, 153	81764	164	85608	157		
81391	14, 153	81770	156	85612	160		
81400	11, 150	81800	156	85613	157		
81404	11, 150	81805	156	85617	164		
81405	12, 151	81807	156	• 85651	10, 149		
81407	11, 150	81810	156	85700	11, 150		
81409	11, 150	81819	156	85701	11, 150		
81410	12, 151	81837	156	• 85702	10, 149		
81411	15, 154	81869	162	• 85703	10, 149		
81412	10, 149	81876	163	85705	160		
81413	12, 151	81877	162	85707	161		
81414	12, 150	81883	162	85712	160		
81422	14, 153	81884	162	• 85718	7		
81427	12, 151	81887	162	• 85722	11, 149		
81448	163	81890	162	• 85723	11, 149		
81450	162	81892	162	• 85724	10, 149		
81451	163	81893	162	• 85730	10, 149		
81452	163	81896	162	• 85734	10, 149		
81456	163	81900	162	85757	157		

• *New Item*



Call 1-800-999-2226 or visit www.westinghouselighting.com.

®, WESTINGHOUSE, and INNOVATION YOU CAN BE SURE OF are trademarks of Westinghouse Electric Corporation.
Used under license by Westinghouse Lighting. All Rights Reserved.