


PERFORMANCE WITH *Style*™

HINKLEY

L I G H T I N G



PERFORMANCE
WITH
Style[™]

THIS SOURCEBOOK CONTAINS A COMPILATION OF THE NEWEST PERFORMANCE GRADE DECORATIVE PRODUCTS FROM HINKLEY LIGHTING, HIGHLIGHTING THE TRADITION OF SOPHISTICATED STYLES AND OUTSTANDING QUALITY COMBINED WITH INDUSTRY-LEADING INNOVATIVE TECHNOLOGY.

CONTACT HINKLEY TO REQUEST A CUSTOM ORDER TO MEET YOUR PROJECT'S NEEDS, WITH CAPABILITIES INCLUDING LAMPING, OPERATING VOLTAGE, LIGHT COLOR, DIMMING AND OTHER PRODUCT-SPECIFIC SPECIAL FEATURES.

CONTENTS

ICONS *and* FINISHES

Throughout this catalog we have utilized a variety of important icons and finish codes to assist you with your lighting selections. Below is a key describing each of these icons in detail as well as a list of our product finishes with abbreviated codes for easy reference.



120 VOLT

Indicates a line voltage fixture that is able to accommodate lamps with a higher wattage and light output. Ideal for commercial and public spaces.



ADA COMPLIANT

Indicates fixtures that adhere to the standards and guidelines listed by the Americans with Disabilities Act.



DARK SKY

Indicates fixtures that are engineered to minimize light glare upward into the night sky.



FIXTURE EXCEEDS 50LBS.

Indicates fixtures weighing over 50lbs. Fixtures must be supported independently of the outlet box unless the outlet box is UL listed for the appropriate weight. Required hardware included.



INVISI-MOUNT

Indicates fixtures where the mounting hardware is hidden on the back plate.



LED

Fixtures come equipped with a fully integrated LED panel and built-in driver.



QUICKFIT

Fixtures recommended for use with QuickFit recessed can light converter kit.



TITLE 24

Title 24 is a state of California Residential Energy Code updated every three years. It applies to any project under review through a building permit. Designated LED and GU24 products meeting Title 24 also qualify for Title 21 Commercial use.

AN	ANTIQUÉ NICKEL
BK	BLACK
BN	BRUSHED NICKEL
BR	BRUSHED BRONZE
BZ	BRONZE
CM	CHROME
DZ	AGED ZINC
HE	HEMATITE
KZ	BUCKEYE BRONZE
LA	LIGHT ALMOND
MZ	MATTE BRONZE
OB	OLDE BRONZE
OZ	OIL RUBBED BRONZE
PN	POLISHED NICKEL
PNI	POLISHED NICKEL
SK	SATIN BLACK
ST	SANDSTONE
SW	SATIN WHITE
TT	TITANIUM

INTERIOR COLLECTIONS

AVENUE	26
ENSEMBLE	04
FULTON	06
HADLEY	22
HALSEY	25
HARRISON	18
HATHAWAY	23
RIGBY	14
WESTON	24

BATH COLLECTIONS

ACCLAIM	31
FAIRLANE	32
PORTIA	28
TREMONT	29
UNITY	30

OUTDOOR + LANDSCAPE COLLECTIONS

OUTDOOR

ATLANTIS	44
HORIZON	38
LUNA	46
PLAZA	45
SHELTER	36
VISTA	42
VUE	40
WESTPORT	34

LANDSCAPE

ATLANTIS	50
DORIAN	51
LUNA	49
LUNA STEP	54
NEXUS	53
NUVI	52
SHELTER	44
SOLARA	51



LED-ING *the way*

HINKLEY'S GUIDE TO OUR INDUSTRY LEADING, ENERGY-EFFICIENT LED LIGHT SOURCES

INTELLIGENT LIGHTING HINKLEY IS DEDICATED TO PROVIDING STATE-OF-THE-ART PRODUCTS BY UTILIZING THE LATEST TECHNOLOGY AND CUTTING EDGE COMPONENTS. BELOW ARE THE ENGINES AND SPECIFICATIONS FOR HINKLEY'S INTEGRATED LED.

ITEM	DESCRIPTION	ENGINE LUMENS	COLOR TEMP.	CRI	WATTS CONSUMED	VA	SYSTEM EFFICACY	INCANDESCENT EQUIVALENCY	DIMMABLE	LIFESPAN
27G2SE-35	Integrated MR Lamp Engine	**	2700K	80	5w	5.3VA		50w	-	60,000 Hrs.
COL-35*	Integrated LED Array	250	2700K	90	5.5w		>45	35w	ANY***	60,000 Hrs.
COL-50*	Integrated LED Array	360	2700K	90	9w		>45	50w	ANY***	50,000 Hrs.
LESF-100	Integrated LED Array	930	2700K	91	16w		>58	100w	ANY***	40,000 Hrs.
LESF-W100	Integrated LED Array	800	2700K	91	16w		>50	75w	ANY***	40,000 Hrs.
LESM-100*	Integrated LED Engine	900	2700K	92	15w		>60	100w	ANY***	40,000 Hrs.
LS-4	Integrated Low Voltage Step Light Engine	200	2700K	90	3.8w	6.5VA		20w	MLV****	40,000 Hrs.
LS-20	Integrated Line Voltage Step Light Engine	240	2700K	90	4w	-		20w	ANY***	40,000 Hrs.
NX4	Integrated Linear Engine	140	2700K	80	1.9w	2.8VA		15w	MLV****	40,000 Hrs.
NX6	Integrated Linear Engine	250	2700K	80	3.8w	5.7VA		25w	MLV****	40,000 Hrs.
NX12	Integrated Linear Engine	500	2700K	80	7.3w	10.8VA		50w	MLV****	40,000 Hrs.

*Fixtures using this integrated technology are protected by U.S. Patents Nos. 8,794,788 and 8,882,293. Other U.S. and foreign patents pending.

Varies by beam spread, see photometrics. *ANY: Any phase cut incandescent dimmer control. ****MLV: Magnetic Low Voltage control on primary (120VAC) side of transformer. Values are subject to change, so be sure to reference hinkleylighting.com for the most up-to-date energy-efficient specs. LED components carry a 5-year limited warranty.

CHANDELIER COLLECTIONS

AVENUE	26
ENSEMBLE	04
FULTON	06
HADLEY	22
HALSEY	25
HARRISON	18
HATHAWAY	23
RIGBY	14
WESTON	24



ENSEMBLE™

FR FREDRICK RAMOND
Hinkley's luxury line

ENSEMBLE'S DARING SILHOUETTE COMBINES LAYERS OF SLEEK EDGES WITH A GLEAMING POLISHED NICKEL FINISH TO CREATE A CAPTIVATING FORM FROM ANY ANGLE.

FR42448PNI
28" W, 46.5" H
71.5" MAX. HEIGHT*
5" SQUARE CANOPY
7-100W MEDIUM

FR42449PNI
32.5" W, 52.5" H
89.5" MAX. HEIGHT*
5" SQUARE CANOPY
13-75W MEDIUM
Fixture exceeds 50lbs.



Ensemble stem hung fixtures are provided with 10' of wire and the following stems: (1) 4", (1) 6" and (2) 12"


*Maximum achievable height with stems included. Additional 12" stems are available: **FR86212PNI**

Bulb specifications indicate maximum wattage.

FR42449PNI [32.5" W, 52.5" H]

OBJECT OF OUR
AFFECTION

*Sculptural statement pieces
inspire art-worthy installation in
spacious entryways and foyers*



FR42448PNI [28" W, 46.5" H]

FULTON™

FINISH BRONZE WITH HERITAGE BRASS
SHADE MOCHA LINEN WITH ESPRESSO TRIM

Fulton's minimalist beauty emphasizes 'less is more' with vintage industrial style. This clean, airy tapered cage design is constructed without glass.

OBJECT OF OUR
AFFECTION

Tapered tiers of multiple cage construction form a unique industrial-inspired installation



3358 BZ
33½" W, 54¾" H
93¾" MAX. H*

50



3357 BZ
27¾" W, 46¼" H
85¼" MAX. H*




3351 BZ
10" W, 12½" H
51¼" MAX. H*



3336 BZ
22" W, 24½" H
69¼" MAX. H*

ITEM	BULBS	CANOPY	WIRE	STEMS INCLUDED	ADDITIONAL FINISHES
3336 BZ	4-60w Cand.	5" Dia.	10'	1-6", 3-12"	DZ
3351 BZ	1-100w Med.	5" Dia.	10'	1-6", 1-12", 1-18"	DZ
3357 BZ	7-100w Med.	5" Dia.	10'	1-6", 1-12", 1-18"	DZ
3358 BZ	13-75w Med.	5" Dia.	10'	1-6", 1-12", 1-18"	DZ

*Maximum achievable height with stems included. Additional 12" stems available. For 3336 BZ and 3351 BZ use 6035 HB. For 3357 BZ and 3358 BZ use 6065 HB. Ideal for vintage filament bulbs (not included).



3334 BZ
18" W, 16¼" H
61" MAX. H*



3337 BZ
10" W, 8¾" H
53½" MAX. H*



3330 BZ
7½" W, 22¼" H



3330 BZ
(side view)



3338 BZ
48" W, 15¾" H
60¾" MAX. H*

ITEM	BULBS	DEPTH	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE	STEMS INCLUDED	ADDITIONAL FINISHES
3330 BZ	2-60w Cand.		5"	11¼"	7½" W, 22¼" H Back Plate			DZ
3334 BZ	4-60w Cand.				5" Dia. Canopy	10'	1-6", 3-12"	DZ
3337 BZ	1-100w Med.				5" Dia. Canopy	10'	1-6", 1-12", 1-18"	DZ
3338 BZ	8-60w Cand.	18"			4¾" W, 9½" L Canopy	10'	2-6", 6-12"	DZ

*Maximum achievable height with stems included. Additional 12" stems available, 6035 HB. Ideal for vintage filament bulbs (not included).



3332 BZ
13½" W, 9¼" H



3335 BZ
50" W, 9" H
53" MAX. H*



3355 BZ
65" W, 9¾" H
53¾" MAX. H*

ITEM	BULBS	DEPTH	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE	STEMS INCLUDED	ADDITIONAL FINISHES
3332 BZ	2-60w Cand.		6¼"	5¾"	5" W, 7½" H Back Plate			DZ
3335 BZ	5-100w Med.	10"			4¾" W, 9½" L Canopy	10'	2-6", 6-12"	DZ
3355 BZ	7-100w Med.	10"			4¾" W, 14½" L Canopy	10'	2-6", 6-12"	DZ

*Maximum achievable height with stems included. Additional 12" stems available. For 3335 BZ use 6035 HB, and for 3355 BZ use 6065 HB. Ideal for vintage filament bulbs (not included).

FULTON™

FINISH AGED ZINC WITH ANTIQUE NICKEL
SHADE BLACK LINEN

Fulton's minimalist beauty emphasizes 'less is more' with vintage industrial style. This clean, airy tapered cage design is constructed without glass.



3358 DZ
33½" W, 54¾" H
93¾" MAX. H*

50



3357 DZ
27¾" W, 46¼" H
85¼" MAX. H*




3351 DZ
10" W, 12½" H
51¼" MAX. H*




3336 DZ
22" W, 24½" H
69¼" MAX. H*

ITEM	BULBS	CANOPY	WIRE	STEMS INCLUDED	ADDITIONAL FINISHES
3336 DZ	4-60w Cand.	5" Dia.	10'	1-6", 3-12"	BZ
3351 DZ	1-100w Med.	5" Dia.	10'	1-6", 1-12", 1-18"	BZ
3357 DZ	7-100w Med.	5" Dia.	10'	1-6", 1-12", 1-18"	BZ
3358 DZ	13-75w Med.	5" Dia.	10'	1-6", 1-12", 1-18"	BZ

*Maximum achievable height with stems included. Additional 12" stems available. For 3336 DZ and 3351 DZ use 6035 AN. For 3357 DZ and 3358 DZ use 6065 AN. Ideal for vintage filament bulbs (not included).



3334 DZ
18" W, 16¼" H
61" MAX. H*



3337 DZ
10" W, 8¾" H
53½" MAX. H*



3330 DZ
7½" W, 22¼" H




3330 DZ
(side view)



3338 DZ
48" W, 15¾" H
60¾" MAX. H*

ITEM	BULBS	DEPTH	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE	STEMS INCLUDED	ADDITIONAL FINISHES
3330 DZ	2-60w Cand.		5"	11¼"	7½" W, 22¼" H Back Plate			BZ
3334 DZ	4-60w Cand.				5" Dia. Canopy	10'	1-6", 3-12"	BZ
3337 DZ	1-100w Med.				5" Dia. Canopy	10'	1-6", 1-12", 1-18"	BZ
3338 DZ	8-60w Cand.	18"			4¾" W, 9½" L Canopy	10'	2-6", 6-12"	BZ


*Maximum achievable height with stems included. Additional 12" stems available, 6035 AN. Ideal for vintage filament bulbs (not included).



3335 DZ
50" W, 9" H
53" MAX. H*



3332 DZ
13½" W, 9¼" H



3355 DZ
65" W, 9¼" H
53¼" MAX. H*

ITEM	BULBS	DEPTH	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE	STEMS INCLUDED	ADDITIONAL FINISHES
3332 DZ	2-60w Cand.		6¼"	5¾"	5" W, 7½" H Back Plate			BZ
3335 DZ	5-100w Med.	10"			4¾" W, 9½" L Canopy	10'	2-6", 6-12"	BZ
3355 DZ	7-100w Med.	10"			4¾" W, 14½" L Canopy	10'	2-6", 6-12"	BZ

*Maximum achievable height with stems included. Additional 12" stems available. For 3335 DZ use 6035 AN, and for 3355 DZ use 6065 AN. Ideal for vintage filament bulbs (not included).

RIGBY™

FINISH AGED ZINC WITH ANTIQUE NICKEL

Rigby is inspired by the Americana barn light reborn as a chic interior retro classic. Features such as cast socket covers, mesh shades, canopy detail and two-tone finish options combine the best in both vintage and industrial design elements.



4364 DZ
40" W, 7" H
40" MAX. H*



4360 DZ
10" W, 8½" H



4363 DZ
27" W, 16¾" H
49¾" MAX. H*



4367 DZ
10" DIA., 4¼" H
37¼" MAX. H*

ITEM	BULBS	DEPTH	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE	STEMS INCLUDED	ADDITIONAL FINISHES
4360 DZ	1-60w Med.		10"	2½"	5" Dia. Back Plate			KZ, PN
4363 DZ	3-60w Med.				5" Dia. Canopy	10'	1-6", 2-12"	KZ, PN
4364 DZ	3-60w Med.	10"			4¾" W, 9" L Canopy	10'	2-6", 4-12"	KZ, PN
4367 DZ	1-60w Med.				5" Dia. Canopy	10'	1-6", 2-12"	KZ, PN

*Maximum achievable height with stems included. Additional 12" stems available, 6067 DZ. Ideal for vintage filament bulbs (not included).

RIGBY™

FINISH POLISHED NICKEL

Rigby is inspired by the Americana barn light reborn as a chic interior retro classic. Features such as cast socket covers, mesh shades, canopy detail and a sleek Polished Nickel finish combine the best in both vintage and industrial design elements.



4364 PN
40" W, 7" H
40" MAX. H*



4360 PN
10" W, 8½" H



4363 PN
27" W, 16¾" H
49¾" MAX. H*



4367 PN
10" DIA., 4¼" H
37¼" MAX. H*

ITEM	BULBS	DEPTH	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE	STEMS INCLUDED	ADDITIONAL FINISHES
4360 PN	1-60w Med.		10"	2½"	5" Dia. Back Plate			DZ, KZ
4363 PN	3-60w Med.				5" Dia. Canopy	10'	1-6", 2-12"	DZ, KZ
4364 PN	3-60w Med.	10"			4¾" W, 9" L Canopy	10'	2-6", 4-12"	DZ, KZ
4367 PN	1-60w Med.				5" Dia. Canopy	10'	1-6", 2-12"	DZ, KZ

*Maximum achievable height with stems included. Additional 12" stems available, 6067 PN. Ideal for vintage filament bulbs (not included).

HARRISON™

FINISH BUCKEYE BRONZE
SHADE OFF-WHITE LINEN

Harrison's transitional style creates a chic, minimalist silhouette with an edge of urban sophistication. The drum shade offers shadow-less construction and is accentuated by a bold metal ring with cast knob accents supporting an etched acrylic lens providing even and warm light throughout. This clean and current design offers enormous flexibility, adding a fresh appearance to a variety of environments, rooms and décor styles.



3705 KZ
26" DIA., 22" H
61" MAX. H*



3704 KZ
20" DIA., 19½" H
58½" MAX. H*



3701 KZ
15" DIA., 6½" H



3703 KZ
20" DIA., 9¾" H



3700 KZ
11½" W, 7" H



ITEM	BULBS	EXT.	TOP TO OUTLET	BACK PLATE/CANOPY	WIRE	STEMS INCLUDED
3700 KZ	1-60w Cand.	4"	8¼"	5" Dia. Back Plate		
3701 KZ	3-60w Med.			12" Dia. Canopy		
3703 KZ	3-100w Med.			5¾" Dia. Canopy		
3704 KZ	3-100w Med.			5¼" Dia. Canopy	10'	1-6", 2-12"
3705 KZ	3-100w Med.			5¼" Dia. Canopy	10'	1-6", 2-12"

*Maximum achievable height with stems included. Additional 12" stems available, 6066 KZ.



RE-IMAGINE RECESSED LIGHTING WITH AN EASY DECORATIVE UPGRADE

Recessed lighting is a familiar feature throughout many homes. Recessed lighting provides directional light on opposing surfaces, such as countertops and floors. The illumination provided from recessed lights often falls short in providing adequate light across the walls and ceiling. Spaces such as hallways, entryways, kitchens, bathrooms and closets can benefit from the stylish touch of a flush mount, casting light evenly throughout the entire space. Consider replacing existing recessed can lights with ceiling mounted fixtures to update your décor while providing better overall ambient lighting. With the QuickFit recessed light converter kit, it's as easy as 1-2-3! Pencil in this simple project as your next quick weekend task—no remodeling required!



LOOK FOR THE QUICKFIT ICON FOR FIXTURES HINKLEY RECOMMENDS AS DECORATIVE ALTERNATIVES TO RECESSED CAN LIGHTING. THE QUICKFIT KIT MAY ALSO BE ORDERED SEPARATELY, 80100 QF.



CLOCKWISE ABOVE: HATHAWAY 32280B-WH, PAGE S059, HADLEY 3300CM, PAGE 292 IN HINKLEY'S FULL LINE CATALOG AND HADLEY 3308BR, PAGE S058

THE QUICKFIT KIT


ADJUST TO ANY CAN SIZE BETWEEN 4" AND 6"



80100 QF

QUICKFIT RECESSED LIGHT CONVERTER KIT

QUICKFIT INSTALLATION *is easy as 1-2-3!*



STEP 1

Mount QuickFit adjustable bar and screw in socket adapter.



STEP 2

Mount fixture hardware and fixture mounting screws to QuickFit bar.



STEP 3

Wire fixture to socket adapter. Secure fixture with hardware included.

ITEM	SOCKET ADAPTER	FITS CAN SIZE	EXCLUDED CAN TYPES	MAX WEIGHT	MOUNTING STRAP TYPE
80100 QF	Medium Base	4" - 6"	Pop-in	50 lbs.	Any

HADLEY™

FINISH ANTIQUE NICKEL, BRUSHED BRONZE, CHROME, OIL RUBBED BRONZE

GLASS ETCHED OPAL

Hadley is a retro-styled collection available in four classic finish options. The etched opal glass shade features a slim design that will complement a variety of decor. This small-scale fixture packs a big punch - the patented LED technology produces as much light as a 100w bulb while consuming only 1/6 the energy. This fully dimmable collection is suitable for both ceiling and wall mount applications. The scale and performance of this collection lends itself to multiple fixture installations, and it is particularly ideal for converting existing recessed can fixtures.



EXCLUSIVELY AVAILABLE IN **HIGH-PERFORMANCE LED**



3308 AN
3308 AN-QF*
7¾" DIA., 4" H



3308 BR
3308 BR-QF*
7¾" DIA., 4" H



3308 OZ
(shown mounted as a sconce)



3308 CM
3308 CM-QF*
7¾" DIA., 4" H



3308 OZ
3308 OZ-QF*
7¾" DIA., 4" H



ITEM	INTEGRATED LED LIGHT SOURCE	CANOPY	DETAILS
3308 AN	1-16w LESF-100	7¾" Dia.	
3308 AN-QF*	1-16w LESF-100	7¾" Dia.	includes 80100QF recessed light converter kit
3308 BR	1-16w LESF-100	7¾" Dia.	
3308 BR-QF*	1-16w LESF-100	7¾" Dia.	includes 80100QF recessed light converter kit
3308 CM	1-16w LESF-100	7¾" Dia.	
3308 CM-QF*	1-16w LESF-100	7¾" Dia.	includes 80100QF recessed light converter kit
3308 OZ	1-16w LESF-100	7¾" Dia.	
3308 OZ-QF*	1-16w LESF-100	7¾" Dia.	includes 80100QF recessed light converter kit

*3308 XX-QF includes QuickFit recessed light converter kit, 80100 QF, also available separately. See page 21. Hadley 3308 flush mounts are ADA compliant when mounted as a sconce. LED components carry a 5-year limited warranty.

Hathaway's striking design features a blown etched opal or amber glass shade held in place by a heavy gauge metal ring fastened to cast uprights and attached with decorative knobs. This small-scale fixture packs a big punch - the patented LED technology produces as much light as a 100w bulb while consuming only 1/6 the energy. This fully dimmable collection is suitable for both ceiling and wall mount applications. The scale and performance of this collection lends itself to multiple fixture installations, and it is particularly ideal for converting existing recessed can fixtures.

HATHAWAY™

ANTIQUE NICKEL, OLDE BRONZE FINISH
ETCHED, ETCHED AMBER GLASS

EXCLUSIVELY AVAILABLE IN **HIGH-PERFORMANCE LED**



3228 AN
3228 AN-QF*
7" DIA., 3/4" H



3228 OB-WH
3228 OB-WH-QF*
7" DIA., 3/4" H



3228 OB
3228 OB-QF*
7" DIA., 3/4" H



3228 AN
(shown mounted as a sconce)



THE SUGGESTION BOX

Downsized flush mounts provide a decorative alternative to recessed lighting, perfectly illuminating spaces such as hallways, entryways, kitchens, bathrooms and closets.

ITEM	INTEGRATED LED LIGHT SOURCE	CANOPY	DETAILS
3228 AN	1-16w LESF-100	6 1/4" Dia.	
3228 AN-QF*	1-16w LESF-100	6 1/4" Dia.	includes 80100 QF recessed light converter kit
3228 OB	1-16w LESF-100	6 1/4" Dia.	
3228 OB-QF*	1-16w LESF-100	6 1/4" Dia.	includes 80100 QF recessed light converter kit
3228 OB-WH	1-16w LESF-100	6 1/4" Dia.	
3228 OB-WH-QF*	1-16w LESF-100	6 1/4" Dia.	includes 80100 QF recessed light converter kit

*3308 XX-QF includes QuickFit recessed light converter kit, 80100 QF, also available separately. See page 21. Hathaway 3228 flush mounts are ADA compliant when mounted as a sconce. LED components carry a 5-year limited warranty.

WESTON™

FINISH BRUSHED NICKEL, BUCKEYE BRONZE
GLASS ETCHED OPAL

Weston's transitional flush mount style features a blown etched opal glass shade supported by a center ring and three crisp angled arms fastened by decorative knobs. This simple and elegant collection embodies the essence of transitional design, making it the perfect choice for almost any space.



3972 BN
15" DIA., 5¼" H



3972 KZ
15" DIA., 5¼" H



3971 BN
13¼" DIA., 5¼" H



3971 KZ
13¼" DIA., 5¼" H

ITEM	BULBS	CANOPY
3971 BN	2-60w Med.	13¼" Dia.
3971 KZ	2-60w Med.	13¼" Dia.
3972 BN	3-60w Med.	15" Dia.
3972 KZ	3-60w Med.	15" Dia.

Halsey's eye-catching slim profile design is created by the sleek blown etched opal glass shade with vertical sidewalls transitioning to a slightly domed bottom. The intersecting square tube frame follows the contour of the glass shade and invisibly attaches to the canopy, further enhancing this clean and sleek design.

HALSEY™

BRUSHED NICKEL, BUCKEYE BRONZE FINISH
ETCHED OPAL GLASS



4382 BN
17" DIA., 5¼" H



4382 KZ
17" DIA., 5¼" H



4381 BN
13" DIA., 4½" H



4381 KZ
13" DIA., 4½" H

ITEM	BULBS	CANOPY
4381 BN	2-60w Med.	13" Dia.
4381 KZ	2-60w Med.	13" Dia.
4382 BN	3-60w Med.	17" Dia.
4382 KZ	3-60w Med.	17" Dia.

AVENUE™

FINISH BRUSHED NICKEL, OIL RUBBED BRONZE
SHADE LINEN

Avenue offers three distinct silhouettes in Brushed Nickel and Oil Rubbed Bronze to fit any style of décor. The patented LED technology produces as much light as a 100w bulb while consuming only 1/6 the energy. This LED sconce is fully dimmable and ADA compliant.



61111 BN
5" W, 12¾" H
♻️ ♿



61111 OZ
5" W, 12¾" H
♻️ ♿



61033 BN
5" W, 7¾" H
♻️ ♿



61033 OZ
5" W, 7¾" H
♻️ ♿



61222 BN
5" W, 8" H
♻️ ♿



61222 OZ
5" W, 8" H
♻️ ♿

ITEM	INTEGRATED LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE
61033 BN	1-16w LESF-100	3¾"	4"	5" W, 7¾" H
61033 OZ	1-16w LESF-100	3¾"	4"	5" W, 7¾" H
61111 BN	1-16w LESF-100	4"	5"	5" W, 7¾" H
61111 OZ	1-16w LESF-100	4"	5"	5" W, 7¾" H
61222 BN	1-16w LESF-100	4"	4"	5" W, 7¾" H
61222 OZ	1-16w LESF-100	4"	4"	5" W, 7¾" H

LED components carry a 5-year limited warranty.

BATH COLLECTIONS

ACCLAIM	31
FAIRLANE	32
PORTIA	28
TREMONT	29
UNITY	30



PORTIA™

FINISH BRUSHED NICKEL, POLISHED NICKEL
GLASS ETCHED OPAL

Portia's slim profile unifies design and technology. A pair of blown etched opal glass cylinders extends from a center metal fixture body, creating a streamlined cylindrical form. Finished in either Brushed Nickel or Polished Nickel, this eco-efficient linear LED collection is fully dimmable and provides even, warm white light. The raceway back plate and optional junction box cover plate provide multiple mounting opportunities.



52112 PN
19" W, 3" H*
(shown without junction box cover plate)



52112 PN
19" W, 4¾" H



52112 PN
(mounted vertically)



52112 BN
19" W, 3" H*
(shown without junction box cover plate)



52112 BN
19" W, 4¾" H

ITEM	INTEGRATED LED LIGHT SOURCE	ENGINE LUMENS	COLOR TEMP.	CRI	INCANDESCENT EQUIVALENCY	LIFESPAN	EXT.	TOP TO OUTLET	BACK PLATE	INV
52112 BN	15w LED	1200	2700K	90	2-60w	40,000 Hrs.	¾***, 3½"	1½"	6" W, 3" H*	•
52112 PN	15w LED	1200	2700K	90	2-60w	40,000 Hrs.	¾***, 3½"	1½"	6" W, 3" H*	•

*Back plate height is 4¾" when mounted with optional junction box cover plate. **Extension when mounted without optional junction box cover plate. Portia fixtures are fully dimmable. LED components carry a 5-year limited warranty.

Tremont offers a bold silhouette ideal for any transitional décor. The formed linear panel of etched white acrylic creates a soft and seamless appearance while evenly diffusing the eco-efficient LED light source. Offered in Brushed Nickel or Polished Nickel, the shade is secured with sleek metal bands, riveted at each end and framed by a full-length back plate. A raceway back plate allows mounting directly to the wall without the included junction box cover plate, for a more streamlined look.

TREMONT™

BRUSHED NICKEL, POLISHED NICKEL FINISH
ETCHED WHITE ACRYLIC GLASS



51812 PN
(mounted vertically)



51812 PN
16" W, 3½" H*
(shown without junction box cover plate)



51814 PN
29½" W, 4¾" H



51814 BN
29½" W, 3½" H*
(shown without junction box cover plate)



51812 BN
16" W, 4¾" H



ITEM	INTEGRATED LED LIGHT SOURCE	ENGINE LUMENS	COLOR TEMP.	CRI	INCANDESCENT EQUIVALENCY	LIFESPAN	EXT.	TOP TO OUTLET	BACK PLATE	INV
51812 BN	15w LED	1200	2700K	90	2-60w	40,000 Hrs.	2¾"**, 3"	1¼"	16" W, 3½" H*	•
51812 PN	15w LED	1200	2700K	90	2-60w	40,000 Hrs.	2¾"**, 3"	1¼"	16" W, 3½" H*	•
51814 BN	30w LED	2400	2700K	90	4-60w	40,000 Hrs.	2¾"**, 3"	1¼"	29½" W, 3½" H*	•
51814 PN	30w LED	2400	2700K	90	4-60w	40,000 Hrs.	2¾"**, 3"	1¼"	29½" W, 3½" H*	•

*Back plate height is 4¾" when mounted with optional junction box cover plate. **Extension when mounted without optional junction box cover plate. Tremont fixtures are fully dimmable. LED components carry a 5-year limited warranty.

UNITY™

FINISH BRUSHED NICKEL, POLISHED NICKEL

GLASS ETCHED, SILK-SCREENED INSIDE

Unity's minimalist silhouette artfully combines form and function. A sleek cylinder of etched tempered glass, silk-screened white along the inside, is exquisitely captured on each end with solid die cast brackets precisely formed to match the contour of the glass shade. The eco-efficient linear LED light source provides warm white light and is fully dimmable. Offered in Brushed Nickel or Polished Nickel, a raceway back plate allows mounting directly to the wall without the included junction box cover plate, for a clean and minimal look when mounting vertically or horizontally.



55652 PN
16" W, 3" H*


(shown without junction box cover plate)



55654 PN
29½" W, 4¾" H



55652 BN
(mounted vertically)



55654 BN
29½" W, 3" H*

(shown without junction box cover plate)



55652 BN
16" W, 4¾" H



ITEM	INTEGRATED LED LIGHT SOURCE	ENGINE LUMENS	COLOR TEMP.	CRI	INCANDESCENT EQUIVALENCY	LIFESPAN	EXT.	TOP TO OUTLET	BACK PLATE	INV
55652 BN	15w LED	1200	2700K	90	2-60w	40,000 Hrs.	3½", 3¾"	1½"	16" W, 3" H*	•
55652 PN	15w LED	1200	2700K	90	2-60w	40,000 Hrs.	3½", 3¾"	1½"	16" W, 3" H*	•
55654 BN	30w LED	2400	2700K	90	4-60w	40,000 Hrs.	3½", 3¾"	1½"	29½" W, 3" H*	•
55654 PN	30w LED	2400	2700K	90	4-60w	40,000 Hrs.	3½", 3¾"	1½"	29½" W, 3" H*	•

*Back plate height is 4¾" when mounted with optional junction box cover plate. **Extension when mounted without optional junction box cover plate. Unity fixtures are fully dimmable. LED components carry a 5-year limited warranty.

Acclaim is a striking contemporary LED design devoted to modern simplicity. A sleek cylinder of etched tempered glass, silk-screened white along the inside, provides a uniform glow from the soft white eco-efficient LED light source. Simple and elegant die-casted end caps capture the glass shade, attaching it to the full-length back plate. Available in Brushed Nickel or Polished Nickel, the raceway back plate allows mounting directly to the wall without the included junction box cover plate, for a clean and minimal look when mounting vertically or horizontally.

ACCLAIM™

BRUSHED NICKEL, POLISHED NICKEL FINISH
ETCHED, SILK-SCREENED INSIDE GLASS



53842 BN
(mounted vertically)



53842 PN
16" W, 4¾" H



53844 PN
29½" W, 3" H*
(shown without junction box cover plate)



53844 BN
29½" W, 4¾" H



53842 BN
16" W, 3" H*
(shown without junction box cover plate)



ITEM	INTEGRATED LED LIGHT SOURCE	ENGINE LUMENS	COLOR TEMP.	CRI	INCANDESCENT EQUIVALENCY	LIFESPAN	EXT.	TOP TO OUTLET	BACK PLATE	INV
53842 BN	15w LED	1200	2700K	90	2-60w	40,000 Hrs.	3½"**, 3¾"	1½"	16" W, 3" H*	•
53842 PN	15w LED	1200	2700K	90	2-60w	40,000 Hrs.	3½"**, 3¾"	1½"	16" W, 3" H*	•
53844 BN	30w LED	2400	2700K	90	4-60w	40,000 Hrs.	3½"**, 3¾"	1½"	29½" W, 3" H*	•
53844 PN	30w LED	2400	2700K	90	4-60w	40,000 Hrs.	3½"**, 3¾"	1½"	29½" W, 3" H*	•

*Back plate height is 4¾" when mounted with optional junction box cover plate. **Extension when mounted without optional junction box cover plate. Acclaim fixtures are fully dimmable. LED components carry a 5-year limited warranty.

FAIRLANE™

FINISH BRUSHED NICKEL, CHROME

GLASS ETCHED WHITE ACRYLIC

Fairlane features elements of mid-century style updated to contemporary cool. A solid formed metal frame encloses etched white acrylic panels, evenly diffusing the eco-efficient LED light source. The dimmable soft white light complements this retro-inspired design, and is offered in a Brushed Nickel or Chrome finish for a polished appearance. Fairlane may be mounted vertically or horizontally, increasing its versatility.



54812 CM
16" W, 5" H



54812 CM
(mounted vertically)



54814 CM
29½" W, 5" H



54814 BN
29½" W, 5" H



54812 BN
16" W, 5" H



ITEM	INTEGRATED LED LIGHT SOURCE	ENGINE LUMENS	COLOR TEMP.	CRI	INCANDESCENT EQUIVALENCY	LIFESPAN	EXT.	TOP TO OUTLET	BACK PLATE	INV
54812 BN	15w LED	1200	2700K	90	2-60w	40,000 Hrs.	3½"	2½"	16" W, 5" H	•
54812 CM	15w LED	1200	2700K	90	2-60w	40,000 Hrs.	3½"	2½"	16" W, 5" H	•
54814 BN	30w LED	2400	2700K	90	4-60w	40,000 Hrs.	3½"	2½"	29½" W, 5" H	•
54814 CM	30w LED	2400	2700K	90	4-60w	40,000 Hrs.	3½"	2½"	29½" W, 5" H	•

Fairlane fixtures are fully dimmable. LED components carry a 5-year limited warranty.

OUTDOOR + LANDSCAPE COLLECTIONS



OUTDOOR

ATLANTIS	44
HORIZON	38
LUNA	46
PLAZA	45
SHELTER	36
VISTA	42
VUE	40
WESTPORT	34

LANDSCAPE

ATLANTIS	50
DORIAN	51
LUNA	49
LUNA STEP	54
NEXUS	53
NUVI	52
SHELTER	44
SOLARA	51

WESTPORT™

FINISH AGED ZINC, BUCKEYE BRONZE
GLASS ETCHED OR CLEAR FRESNEL LENS

Inspired by ship bulkheads, Westport is a fusion of unique maritime elements. The die-cast aluminum fixture is offered as incandescent with candelabra lamping and a clear glass Fresnel lens, or as an LED version paired with an etched glass Fresnel lens. Bold finish options of Buckeye Bronze or Aged Zinc reinforce its distinctive style.



2722 KZ
11¼" W, 12¾" H





2722 KZ-LED
(mounted flush to ceiling)



**THE
SUGGESTION
BOX**

Use the LED version as a flush mount inside or outdoors! Installed on a ceiling, this creates an unexpected, modern interpretation of the traditional porthole design.



2722 DZ
11¼" W, 12¾" H



2722 KZ-LED
11¼" W, 12¾" H



2722 DZ-LED
11¼" W, 12¾" H



ITEM	BULBS	LED ITEM	INTEGRATED LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE
2722 DZ	2-60w Cand.	2722 DZ-LED	1-16w LESF-W100	4"	7¼"	6½" Dia.
2722 KZ	2-60w Cand.	2722 KZ-LED	1-16w LESF-W100	4"	7¼"	6½" Dia.

SHELTER™

FINISH BLACK, BUCKEYE BRONZE, HEMATITE
GLASS CLEAR SEEDY

Shelter's minimalist style in solid aluminum creates a chic, dramatic statement as the dimmable, LED light source from above grazes through its clear seedy glass. Shelter comes standard Dark Sky compliant.



1344 BK
8" W, 18" H





1344 HE
8" W, 18" H




1344 KZ
8" W, 18" H




1340 BK
6" W, 12" H




1340 HE
6" W, 12" H




1340 KZ
(side view)
6" W, 12" H


ITEM	INTEGRATED LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE
1340 BK	1-16w LESF-W100	3¾"	2½"	6" W, 12" H
1340 HE	1-16w LESF-W100	3¾"	2½"	6" W, 12" H
1340 KZ	1-16w LESF-W100	3¾"	2½"	6" W, 12" H
1344 BK	1-16w LESF-W100	4"	3"	8" W, 18" H
1344 HE	1-16w LESF-W100	4"	3"	8" W, 18" H
1344 KZ	1-16w LESF-W100	4"	3"	8" W, 18" H

HORIZON™

FINISH BLACK, BUCKEYE BRONZE

GLASS CLEAR SEEDY

Horizon's simple elegance emphasizes its dominant expanse of clear seedy glass finished with a flame polished edge. This versatile fixture is constructed of die-cast aluminum and can be mounted horizontally, vertically or on the ceiling. The center band, available in either Buckeye Bronze or Black finish options, is uniquely adjustable to allow flexible mounting options. The open top and bottom maximizes the output of the dimmable LED light source.



2895 BK
5" W, 20½" H




2895 KZ
5" W, 20½" H






2894 BK
5" W, 17" H





2894 KZ
5" W, 17" H




2890 KZ
(mounted horizontally)




2890 BK
5" W, 12" H




2890 KZ
(side view)
5" W, 12" H



THE SUGGESTION BOX



Horizon's adjustable mounting allows you to choose your glass position creating multiple looks with one fixture.*

ITEM	INTEGRATED LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE
2890 BK	1-16w LESF-W100	3½"	4½", 6¼", 7¾"	5" W, 4½" H
2890 KZ	1-16w LESF-W100	3½"	4½", 6¼", 7¾"	5" W, 4½" H
2894 BK	1-16w LESF-W100	3½"	5¾", 8½", 11½"	5" W, 4½" H
2894 KZ	1-16w LESF-W100	3½"	5¾", 8½", 11½"	5" W, 4½" H
2895 BK	1-16w LESF-W100	3½"	7½", 10¼", 13¼"	5" W, 4½" H
2895 KZ	1-16w LESF-W100	3½"	7½", 10¼", 13¼"	5" W, 4½" H

*Multiple top to outlet measurements with adjustable glass positioning.

VUE™

FINISH BRONZE, TITANIUM
GLASS ACRYLIC LENS

Vue's contemporary linear LED design is constructed of extruded and die-cast aluminum and is offered in either Bronze or Titanium finishes. The seamless architectural form emits light from white acrylic side windows and sleek front sliver. Incredibly versatile, the wet-rated Vue can be mounted vertically or horizontally, inside or outdoors.

THE
SUGGESTION
BOX

Vue is the perfect addition to a contemporary bath setting, or as a ceiling mounted fixture.



12314 BZ
5" W, 26" H





12312 TT
(mounted horizontally)



12314 TT
5" W, 26" H



12312 BZ
5" W, 14¾" H



12312 TT
5" W, 14¾" H



ITEM	INTEGRATED LED LIGHT SOURCE	ENGINE LUMENS	COLOR TEMP.	CRI	INCANDESCENT EQUIVALENCY	LIFESPAN	EXT.	TOP TO OUTLET	BACK PLATE
12312 BZ	15w LED	1200	2700K	90	2-60w	40,000 Hrs.	3"	7½"	5" W, 6" H
12312 TT	15w LED	1200	2700K	90	2-60w	40,000 Hrs.	3"	7½"	5" W, 6" H
12314 BZ	30w LED	2400	2700K	90	4-60w	40,000 Hrs.	3"	13"	5" W, 6" H
12314 TT	30w LED	2400	2700K	90	4-60w	40,000 Hrs.	3"	13"	5" W, 6" H

Vue fixtures are fully dimmable. LED components carry a 5-year limited warranty.

VISTA™

FINISH BRONZE, TITANIUM
GLASS ACRYLIC LENS

Vista creates a strong visual statement with an elongated contemporary silhouette. Constructed with extruded and die-cast aluminum, an angled cut-out creates a modern focal point with a resilient acrylic lens for maximum durability. Vista is offered as an energy-saving LED design in either Bronze or Titanium finish options. Incredibly versatile, the wet-rated Vista can be mounted vertically or horizontally, inside or outdoors.

THE
SUGGESTION ▶
BOX

Vista is the perfect addition to a contemporary bath setting, or as a ceiling mounted fixture.



12304 TT
5" W, 29½" H





12302 BZ
(mounted horizontally)



12304 BZ
5" W, 29½" H



12302 TT
5" W, 18¾" H



12302 BZ
5" W, 18¾" H



ITEM	INTEGRATED LED LIGHT SOURCE	ENGINE LUMENS	COLOR TEMP.	CRI	INCANDESCENT EQUIVALENCY	LIFESPAN	EXT.	TOP TO OUTLET	BACK PLATE
12302 BZ	15w LED	1200	2700K	90	2-60w	40,000 Hrs.	3"	9½"	5" W, 6" H
12302 TT	15w LED	1200	2700K	90	2-60w	40,000 Hrs.	3"	9½"	5" W, 6" H
12304 BZ	30w LED	2400	2700K	90	4-60w	40,000 Hrs.	3"	14¾"	5" W, 6" H
12304 TT	30w LED	2400	2700K	90	4-60w	40,000 Hrs.	3"	14¾"	5" W, 6" H

Vista fixtures are fully dimmable. LED components carry a 5-year limited warranty.

ATLANTIS™

FINISH BRONZE, TITANIUM, SATIN BLACK
GLASS ETCHED GLASS LENSES

Atlantis features a minimalist design for the ultimate in urban sophistication. Constructed of solid aluminum and Dark Sky compliant, Atlantis provides a chic solution to eco-conscious homeowners.



1639 BZ
1639 BZ-LED
12" W, 36" H



1639 TT
1639 TT-LED
12" W, 36" H



1639 SK
1639 SK-LED
12" W, 36" H

ITEM	BULBS	LED ITEM	INTEGRATED LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE
1639 BZ	3-50w GU-10*	1639 BZ-LED	3-9w COL-50	4"	31"	4½" W, 6½" H
1639 SK	3-50w GU-10*	1639 SK-LED	3-9w COL-50	4"	31"	4½" W, 6½" H
1639 TT	3-50w GU-10*	1639 TT-LED	3-9w COL-50	4"	31"	4½" W, 6½" H

*GU-10 bulb included.

Plaza features a contemporary form constructed from durable aluminum. This sleek shape creates a unique wall-wash effect with a down light producing a subtle grazing of the center square for a layered sense of illumination.

PLAZA™

BRONZE, TITANIUM FINISH
ETCHED ACRYLIC LENS GLASS



20300 casts light out at 360°



20300 TT
10" W, 10" H



20300 BZ
10" W, 10" H



ITEM	INTEGRATED LED LIGHT SOURCE	ENGINE LUMENS	COLOR TEMP.	CRI	INCANDESCENT EQUIVALENCY	LIFESPAN	EXT.	TOP TO OUTLET	BACK PLATE
20300 BZ	24w LED	1900	2700K	90	2-75w	40,000 Hrs.	4"	5"	6¼" Square
20300 TT	24w LED	1900	2700K	90	2-75w	40,000 Hrs.	4"	5"	6¼" Square

Plaza fixtures are fully dimmable. LED components carry a 5-year limited warranty.

LUNA™

FINISH BRONZE, SATIN BLACK, TITANIUM

GLASS ETCHED GLASS LENSES

Luna is a modern collection of solid aluminum fixtures offered in a unique combination of contemporary styles, including sleek wall lanterns with a dual light source and decorative reflector. Luna also offers chic pocket wall sconces and compact ceiling mounts that are ideal for indoor or out. Luna is standard ADA compliant.



1669 TT

9" W, 24" H






1669 SK
1669 SK-LED
9" W, 24" H




1669 BZ
1669 BZ-LED
9" W, 24" H



1668 TT
1668 TT-LED
6" W, 16" H



1668 SK
1668 SK-LED
6" W, 16" H



1668 BZ
1668 BZ-LED
6" W, 16" H



ITEM	BULBS	LED ITEM	INTEGRATED LED LIGHT SOURCE	EXT.	TOP TO OUTLET	BACK PLATE
1668 BZ	2-20w GU10*	1668 BZ-LED	2-5.5w COL-35	4"	8"	4½" Square
1668 SK	2-20w GU10*	1668 SK-LED	2-5.5w COL-35	4"	8"	4½" Square
1668 TT	2-20w GU10*	1668 TT-LED	2-5.5w COL-35	4"	8"	4½" Square
1669 BZ	2-20w GU10*	1669 BZ-LED	2-5.5w COL-35	4"	12"	4½" Square
1669 SK	2-20w GU10*	1669 SK-LED	2-5.5w COL-35	4"	12"	4½" Square
1669 TT	2-20w GU10*	1669 TT-LED	2-5.5w COL-35	4"	12"	4½" Square

*GU10 bulb included.



Introducing...

BRAND NEW BOLLARDS

STREAMLINED DESIGN + DURABILITY + EFFICIENT LIGHT OUTPUT



COORDINATING OUTDOOR LANTERN
COLLECTIONS ARE AVAILABLE FOR
ALL BOLLARDS.

LUNA BOLLARD IN
BRONZE AND TITANIUM,
SEE PAGE 49



15609 BZ
15609 BZ-LED
LUNA™ BOLLARD
3" DIA., 30" H



15609 TT
15609 TT-LED
LUNA™ BOLLARD
3" DIA., 30" H



15607 KZ
15607 KZ-LED
SHELTER™ BOLLARD
4" W, 30" H



15607 HE
15607 HE-LED
SHELTER™ BOLLARD
4" W, 30" H



15607 BK
15607 BK-LED
SHELTER™ BOLLARD
4" W, 30" H



LED ITEM	LED ENGINE (INCLUDED)	POWER SUPPLY REQUIREMENT	INCANDESCENT EQUIVALENCY	ITEM	LAMP (NOT INCLUDED)	MAX. WATTAGE	FINISH	CONSTRUCTION	LENS
15607 BK-LED	27G2SE-35	5w / 5.3VA	35w	15607 BK	MR16	35w	Black	Aluminum	Clear Acrylic Outside Cylinder Seedy Glass Inside Panel
15607 HE-LED	27G2SE-35	5w / 5.3VA	35w	15607 HE	MR16	35w	Hematite	Aluminum	Clear Acrylic Outside Cylinder Seedy Glass Inside Panel
15607 KZ-LED	27G2SE-35	5w / 5.3VA	35w	15607 KZ	MR16	35w	Buckeye Bronze	Aluminum	Clear Acrylic Outside Cylinder Seedy Glass Inside Panel
15609 BZ-LED	27G2SE-35	5w / 5.3VA	35w	15609 BZ	MR16	50w	Bronze	Aluminum	Etched Glass
15609 TT-LED	27G2SE-35	5w / 5.3VA	35w	15609 TT	MR16	50w	Titanium	Aluminum	Etched Glass

A wiring kit and universal bollard mount with 2" power post are supplied. For lampping options (not included), accessories and transformers, see Hinkley's Landscape Lighting catalog.

BOLLARDS



15601 BZ
15601 BZ-LED
ATLANTIS™
ROUND BOLLARD
3" DIA., 30" H



15601 TT
15601 TT-LED
ATLANTIS™
ROUND BOLLARD
3" DIA., 30" H



15602 BZ
15602 BZ-LED
ATLANTIS™
SQUARE BOLLARD
3" SQ., 30" H



15602 TT
15602 TT-LED
ATLANTIS™
SQUARE BOLLARD
3" SQ., 30" H



LED ITEM	LED ENGINE (INCLUDED)	POWER SUPPLY REQUIREMENT	INCANDESCENT EQUIVALENCY	ITEM	LAMP (NOT INCLUDED)	MAX. WATTAGE	FINISH	CONSTRUCTION	LENS
15601 BZ-LED	27G2SE-35	5w / 5.3VA	35w	15601 BZ	MR16	50w	Bronze	Aluminum	Etched Glass
15601 TT-LED	27G2SE-35	5w / 5.3VA	35w	15601 TT	MR16	50w	Titanium	Aluminum	Etched Glass
15602 BZ-LED	27G2SE-35	5w / 5.3VA	35w	15602 BZ	MR16	50w	Bronze	Aluminum	Etched Glass
15602 TT-LED	27G2SE-35	5w / 5.3VA	35w	15602 TT	MR16	50w	Titanium	Aluminum	Etched Glass

A wiring kit and universal bollard mount with 2" power post are supplied. For lampping options (not included), accessories and transformers, see Hinkley's Landscape Lighting catalog.



15604 BZ
15604 BZ-LED
SOLARA™ BOLLARD
3" DIA., 30" H



15604 TT
15604 TT-LED
SOLARA™ BOLLARD
3" DIA., 30" H



15612 BZ
15612 BZ-LED
DORIAN™ BOLLARD
3" SQ., 30" H



15612 TT
15612 TT-LED
DORIAN™ BOLLARD
3" SQ., 30" H



LED ITEM	LED ENGINE (INCLUDED)	POWER SUPPLY REQUIREMENT	INCANDESCENT EQUIVALENCY	ITEM	LAMP (NOT INCLUDED)	MAX. WATTAGE	FINISH	CONSTRUCTION	LENS
15604 BZ-LED	27G2SE-35	5w / 5.3VA	35w	15604 BZ	MR16	50w	Bronze	Aluminum	White Acrylic
15604 TT-LED	27G2SE-35	5w / 5.3VA	35w	15604 TT	MR16	50w	Titanium	Aluminum	White Acrylic
15612 BZ-LED	27G2SE-35	5w / 5.3VA	35w	15612 BZ	MR16	50w	Bronze	Aluminum	Etched Glass
15612 TT-LED	27G2SE-35	5w / 5.3VA	35w	15612 TT	MR16	50w	Titanium	Aluminum	Etched Glass

A wiring kit and universal bollard mount with 2" power post are supplied. For lamplng options (not included), accessories and transformers, see Hinkley's Landscape Lighting catalog.




15446 BZ
15446 BZ-10
5" L, 3" W, 3/4" H
2 1/8" BRACKET DEPTH



NUVI HARDSCAPE

- + Exceptional 12v led horizontal illumination due to innovative composite optic technology
- + Durable, solid vinyl alloy construction tested for 20 years of color life
- + Diverse range of mounting opportunities
- + Easy and efficient installation: fewer fixtures illuminate a more extensive area
- + Suitable for harsh environments
- + ETL rated for indoor/outdoor use
- + Available as single items or packages of 10



15446 ST
15446 ST-10
5" L, 3" W, 3/4" H
2 1/8" BRACKET DEPTH



15446 TT
15446 TT-10
5" L, 3" W, 3/4" H
2 1/8" BRACKET DEPTH



LED ITEM	LED ENGINE (INCLUDED)	POWER SUPPLY REQUIREMENT	INCANDESCENT EQUIVALENCY	FINISH	CONSTRUCTION	LENS
15446 BZ, 15446 BZ-10	NX4	1.9w / 2.8VA	15w	Bronze	Vinyl Alloy	Composite PC
15446 ST, 15446 ST-10	NX4	1.9w / 2.8VA	15w	Sandstone	Vinyl Alloy	Composite PC
15446 TT, 15446 TT-10	NX4	1.9w / 2.8VA	15w	Titanium	Vinyl Alloy	Composite PC

Nuvi Hardscape carries a 10 year limited warranty.



DESIGN NOTE

Linear head rotates 360° for precise adjustments

15442 BZ
LARGE HARDSCAPE DECK LIGHT
15½" W, 1⅜" H
3½" BRACKET DEPTH



15442 SW
LARGE HARDSCAPE DECK LIGHT
15½" W, 1⅜" H
3½" BRACKET DEPTH



15440 SW
SMALL HARDSCAPE DECK LIGHT
9½" W, 1⅜" H
3½" BRACKET DEPTH



15440 BZ
SMALL HARDSCAPE DECK LIGHT
9½" W, 1⅜" H
3½" BRACKET DEPTH



HARDSCAPE SPACING RECOMMENDATIONS

MOUNTING HEIGHT	15440BZ/SW CENTER TO CENTER	15442BZ/SW CENTER TO CENTER
1'	2'	3'
2'	3'	4'
3'	4'	6'



NEXUS HARDSCAPE LIGHTS ARE PROVIDED WITH A REMOVABLE MOUNTING PLATE


LED ITEM	LED ENGINE (INCLUDED)	POWER SUPPLY REQUIREMENT	INCANDESCENT EQUIVALENCY	FINISH	CONSTRUCTION	LENS
15440 BZ	NX6	3.8w / 5.7VA	25w	Bronze	Aluminum	Polycarbonate
15440 SW	NX6	3.8w / 5.7VA	25w	Satin White	Aluminum	Polycarbonate
15442 BZ	NX12	7.3w / 10.8VA	50w	Bronze	Aluminum	Polycarbonate
15442 SW	NX12	7.3w / 10.8VA	50w	Satin White	Aluminum	Polycarbonate

A wiring kit and ground spike are supplied. For accessories and transformers, see Hinkley's Landscape Lighting catalog.



NOW AVAILABLE IN 12V

LUNA STEP LIGHT



- + FULLY DIMMABLE
- + FITS STANDARD GANG JUNCTION BOX
- + 3.8W POWER CONSUMPTION
- + DIE CAST ZINC ALUMINUM ALLOY

120V LUNA STEP LIGHTS

are available in five finishes in both single and double gang configurations. SEE PAGES

57-59.





15508 SW
12V LUNA™ STEP LIGHT
4½" W, 3" H



15508 MZ
12V LUNA™ STEP LIGHT
4½" W, 3" H



KNOW YOUR MATERIAL

Matte BRONZE finish features a forged BRASS face plate



15508 BZ
12V LUNA™ STEP LIGHT
4½" W, 3" H



15508 TT
12V LUNA™ STEP LIGHT
4½" W, 3" H




LED ITEM	LED ENGINE (INCLUDED)	POWER SUPPLY REQUIREMENT	INCANDESCENT EQUIVALENCY	FINISH	CONSTRUCTION
15508 BZ	LS-4	3.8w / 6.5VA	20w	Bronze	Zinc Aluminum Alloy
15508 MZ	LS-4	3.8w / 6.5VA	20w	Matte Bronze	Forged Brass Face Plate
15508 SW	LS-4	3.8w / 6.5VA	20w	Satin White	Zinc Aluminum Alloy
15508 TT	LS-4	3.8w / 6.5VA	20w	Titanium	Zinc Aluminum Alloy

For line voltage accessories and transformers, see Hinkley's Landscape Lighting catalog.

PHOTOMETRICS (BASED ON VARIOUS MOUNTING HEIGHTS)

DISTANCE FROM LIGHT		LED ITEM	1'	2'	3'	4'	5'	6'	7'	8'	
FOOT CANDLES	8" Mounting	15508 BZ	3.58	0.71	0.2						
	16" Mounting			0.86	0.38	0.15					
	30" Mounting				0.27	0.24	0.13				
	8" Mounting	15508 MZ	3.58	0.71	0.20						
	16" Mounting			0.86	0.38	0.15					
	30" Mounting				0.27	0.24	0.13				
	8" Mounting	15508 SW	7	2.19	0.97	0.57	0.37	0.26	0.19	0.14	
	16" Mounting			0.66	0.158	0.85	0.5	0.32	0.23	0.16	0.12
	30" Mounting				0.32	0.52	0.43	0.3	0.23	0.16	0.12
	8" Mounting	15508 TT	4.5	1.8	0.45	0.25	0.15	0.11			
	16" Mounting				1.03	0.54	0.27	0.15	0.1		
	30" Mounting					0.32	0.29	0.19	0.12		





THE PERFECT SOLUTION FOR ANY INDOOR OR OUTDOOR
120V OUTLET OR SWITCH LOCATION

- + FULLY DIMMABLE
- + FITS STANDARD GANG JUNCTION BOX
- + 4W POWER CONSUMPTION
- + DIE CAST ZINC ALUMINUM ALLOY
- + INDOOR/OUTDOOR ETL RATED



58504 BZ
120V LUNA™ STEP LIGHT
3" W, 4½" H



58504 LA
120V LUNA™ STEP LIGHT
3" W, 4½" H



58504 MZ
120V LUNA™ STEP LIGHT
3" W, 4½" H



58504 SW
120V LUNA™ STEP LIGHT
3" W, 4½" H



58504 TT
120V LUNA™ STEP LIGHT
3" W, 4½" H



LED ITEM	LED ENGINE (INCLUDED)	WATTAGE	INCANDESCENT EQUIVALENCY	FINISH	CONSTRUCTION
58504 BZ	LS-20	4w	20w	Bronze	Zinc Aluminum Alloy
58504 LA	LS-20	4w	20w	Light Almond	Zinc Aluminum Alloy
58504 MZ	LS-20	4w	20w	Matte Bronze	Forged Brass Face Plate
58504 SW	LS-20	4w	20w	Satin White	Zinc Aluminum Alloy
58504 TT	LS-20	4w	20w	Titanium	Zinc Aluminum Alloy

For line voltage accessories and transformers, see Hinkley's Landscape Lighting catalog.

PHOTOMETRICS (BASED ON VARIOUS MOUNTING HEIGHTS)

DISTANCE FROM LIGHT		LED ITEM	1'	2'	3'	4'	5'	6'	7'	8'
FOOT CANDLES	8" Mounting	58504 BZ	6.36	1.01	0.22					
	16" Mounting		2.6	1.65	0.67	0.3	0.13			
	30" Mounting		0.16	1.1	0.69	0.4	0.23	0.13		
	8" Mounting	58504 LA	8.79	2.0	0.79	0.38	0.21	0.13	0.09	
	16" Mounting		3.03	2.12	0.89	0.43	0.23	0.14	0.06	
	30" Mounting			1.14	0.81	0.45	0.28	0.16	0.11	0.08
	8" Mounting	58504 MZ	6.74	1.12	0.24					
	16" Mounting		2.73	1.82	0.73	0.31	0.14			
	30" Mounting			1.22	0.76	0.40	0.23	0.12		
	8" Mounting	58504 SW	9.29	2.6	1.17	0.64	0.42	0.29	0.21	0.16
	16" Mounting		3.0	2.32	1.17	0.66	0.41	0.28	0.2	0.15
	30" Mounting		0.25	1.19	0.93	0.6	0.4	0.29	0.21	0.16
8" Mounting	58504 TT	9.05	2.2	0.83	0.4	0.25	0.16	0.11		
16" Mounting		3.16	2.17	0.97	0.49	0.27	0.16	0.1		
30" Mounting		0.1	1.29	0.86	0.52	0.33	0.22	0.15	0.1	

LUNA™ STEP 120V



58508 BZ
120V LUNA™ STEP LIGHT
4½" W, 3" H



58508 LA
120V LUNA™ STEP LIGHT
4½" W, 3" H



58508 SW
120V LUNA™ STEP LIGHT
4½" W, 3" H



KNOW YOUR MATERIAL


58504 MZ and 58508 MZ feature a forged brass face plate



58508 MZ
120V LUNA™ STEP LIGHT
4½" W, 3" H



58508 TT
120V LUNA™ STEP LIGHT
4½" W, 3" H



LED ITEM	LED ENGINE (INCLUDED)	POWER SUPPLY REQUIREMENT	INCANDESCENT EQUIVALENCY	FINISH	CONSTRUCTION
58508 BZ	LS-20	4w	20w	Bronze	Zinc Aluminum Alloy
58508 LA	LS-20	4w	20w	Light Almond	Zinc Aluminum Alloy
58508 MZ	LS-20	4w	20w	Matte Bronze	Forged Brass Face Plate
58508 SW	LS-20	4w	20w	Satin White	Zinc Aluminum Alloy
58508 TT	LS-20	4w	20w	Titanium	Zinc Aluminum Alloy

For line voltage accessories and transformers, see Hinkley's Landscape Lighting catalog.

PHOTOMETRICS (BASED ON VARIOUS MOUNTING HEIGHTS)

DISTANCE FROM LIGHT		LED ITEM	1'	2'	3'	4'	5'	6'	7'	8'	
FOOT CANDLES	8" Mounting	58508 BZ	3.58	0.71	0.2						
	16" Mounting			0.86	0.38	0.15					
	30" Mounting				0.27	0.24	0.13				
	8" Mounting	58508 LA	4.41	1.64	0.32	0.24	0.13	0.09			
	16" Mounting			0.97	0.50	0.26	0.14	0.10			
	30" Mounting				0.29	0.27	0.18	0.12			
	8" Mounting	58508 MZ	3.79	0.79	0.23						
	16" Mounting			0.90	0.41	0.17					
	30" Mounting				0.33	0.29	0.14				
	8" Mounting	58508 SW	7.0	2.19	0.97	0.57	0.37	0.26	0.19	0.14	
	16" Mounting			0.66	0.158	0.85	0.5	0.32	0.23	0.16	0.12
	30" Mounting				0.32	0.52	0.43	0.3	0.23	0.16	0.12
8" Mounting	58508 TT	4.5	1.8	0.45	0.25	0.15	0.11				
16" Mounting				1.03	0.54	0.27	0.15	0.1			
30" Mounting					0.32	0.29	0.19	0.12			



58506 BZ
120V LUNA™ STEP LIGHT
4¾" W, 4½" H




58506 LA
120V LUNA™ STEP LIGHT
4¾" W, 4½" H



DOUBLE GANG configuration



58506 SW
120V LUNA™ STEP LIGHT
4¾" W, 4½" H



58506 TT
120V LUNA™ STEP LIGHT
4¾" W, 4½" H



LED ITEM	LED ENGINE	WATTAGE	INCANDESCENT EQUIVALENCY	FINISH	CONSTRUCTION
58506 BZ	LS-20	4w	20w	Bronze	Zinc Aluminum Alloy
58506 LA	LS-20	4w	20w	Light Almond	Zinc Aluminum Alloy
58506 SW	LS-20	4w	20w	Satin White	Zinc Aluminum Alloy
58506 TT	LS-20	4w	20w	Titanium	Zinc Aluminum Alloy

For line voltage accessories and transformers, see Hinkley's Landscape Lighting catalog.

PHOTOMETRICS (BASED ON VARIOUS MOUNTING HEIGHTS)

DISTANCE FROM LIGHT		LED ITEM	1'	2'	3'	4'	5'
FOOT CANDLES	8" Mounting	58506 BZ	4.76	0.47	0.08		
	16" Mounting		2.24	0.92	0.17	0.06	
	30" Mounting		1.08	0.65	0.21	0.11	0.03
	8" Mounting	58506 LA	6.33	0.84	0.21	0.08	
	16" Mounting		4.11	1.22	0.34	0.13	0.09
	30" Mounting		2.47	0.83	0.46	0.15	0.06
	8" Mounting	58506 SW	7.15	0.89	0.20	0.08	
	16" Mounting		3.22	0.77	0.31	0.14	0.07
	30" Mounting		2.12	0.81	0.26	0.15	0.06
	8" Mounting	58506 TT	6.86	0.70	0.16	0.06	
	16" Mounting		2.97	1.13	0.39	0.11	0.05
	30" Mounting		1.88	0.95	0.23	0.14	0.06



PERFORMANCE
WITH
Style[™]

BE ON THE LOOKOUT FOR HINKLEY'S BRAND NEW "PERFORMANCE WITH STYLE"
FULL LINE CATALOG COMING IN 2016.

FIND LIGHTING TO PERFECT EVERY PROJECT | HINKLEYLIGHTING.COM

THIS IS HINKLEY

At your fingertips | AWARD-WINNING CATALOGS

Check out our full range of products in easy-to-use, full color catalogs complete with sizing guidelines, design ideas and eco-tips.

Information 24/7/365 | DYNAMIC WEBSITE

hinkleylighting.com

Surf all of the details on our lighting collections, including the newest products from Hinkley and Fredrick Ramond, tips from professional designers and locate a Hinkley showroom in your area.

Make the world a better place | COMMUNITY INVOLVEMENT

The Hinkley Lighting family proudly supports breast cancer initiatives. By increasing awareness and supporting education and community events, together we can work towards finding a cure. Hinkley also supports a variety of other charitable organizations that strive to make a positive difference in the lives of others. Visit hinkleylighting.com for more information.

Be inspired | ENGAGING VIDEOS

youtube.com/hinkleylightinginc

Visit Hinkley on YouTube to watch our product, educational and brand videos.

Talk is chic | SOCIAL MEDIA

See what captivates us:

facebook.com/hinkleylighting

pinterest.com/hinkleylighting

houzz.com/hinkleylighting

instagram.com/hinkleylighting

twitter.com/hinkleylighting



Hinkley Lighting stands behind the quality of our lighting fixtures with product warranties that are among the strongest in the industry. For details of warranty coverage on specific products, please refer to hinkleylighting.com or consult a qualified Hinkley retail distributor.

Several Hinkley Lighting products are protected under U.S. Patent and foreign patent, or patent pending. For current information regarding Hinkley Lighting's patent portfolio, please visit hinkleylighting.com.

©2016 Hinkley Lighting, Inc.
All rights reserved in all copyrightable works.

american
lighting
association

Hinkley Lighting is a proud partner
of the American Lighting Association.

HINKLEY

L I G H T I N G

CLASSIC, CHIC COLLECTIONS | HINKLEYLIGHTING.COM



FREDRICK RAMOND

ESTABLISHED 1965

HINKLEY'S LUXURY LINE | FREDRICKRAMOND.COM