

The background is a deep forest green with several large, overlapping, organic shapes that resemble liquid or smoke. These shapes are slightly darker or lighter than the base color, creating a sense of depth and movement. The overall effect is modern and sophisticated.

WAC
LANDSCAPE LIGHTING

ABOUT WAC LANDSCAPE LIGHTING

Dream it. Solve it. Make it.

WAC LIGHTING is a second generation family-owned and operated lighting company with a reputation for quality spanning over 30 years. We have a history of inventing and making technology leveraged innovation widely available to the market through unbelievably competitive pricing and reputable distribution partnerships.

Our choice has consistently been to operate at a higher level of responsibility, giving our customers the true benefits of a world class factory-direct relationship.

Headquartered in New York, we have factories in New York, California, Georgia, and China to support a fully vertically-integrated research, design, engineering, electronics, fabrication, manufacturing, and testing operation worldwide.

WAC LANDSCAPE LIGHTING is an expansion of our lighting technology brand to offer ground-breaking new patented solutions to the irrigation and green industry that address problems currently not addressed by other landscape lighting companies.

We invite you to get excited. The wait is finally over.

Table of Contents

LED Hardscape	5-8	LED Step Lights	39-42
LED Grand Accent	9-10	LED Path Lights	43-62
LED Accent	11-12	LED Bollards.....	63-72
LED Mini Accent.....	13-16	Transformers/Accessories	73-74
LED Mini Wall Wash	17-18	120V CREW	
LED Wall Wash	19-20	LED FUNCTIONAL DIRECT-WIRE LIGHTING	
LED 3" In-Ground	21-24	LED Landscape	75-76
LED ilumenight™ Color Changing	25-26	LED Outdoor Tape Light	77-80
LED Underwater Spot	27-28	LED Brick Lights.....	81-82
LED Submersible 2" Ingrounds	29-30	LED Flood Lights.....	83-88
LED Recessed Ingrounds + Indicator	31-34	LED Wall Packs	89-90
12V LED Outdoor Tape Light	35-36	LED Decorative.....	91-94
LED Deck & Patio	37-38	Photometrics.....	95-103

LANDSCAPE

Durability. Flexibility. Guaranteed.

Every WAC Lighting fixture in our patent pending line of technology landscape products is thoroughly tested in our nationally recognized NVLAP, UL, and ETL certified laboratories for safety, durability, and robust long term performance even in the most rugged environments.



Listed to UL 1838 standard (12V)
1598 standard (120V)

LED Life Expectancy

Rated life of LED lights are based on IES (Illuminating Engineering Society) L70 standard accelerated lifetime testing for how long they will operate until only 70% of the original light output remains .

There is No Equal

Mini Accent, Accent & Grand Accent:

BRIGHTNESS

With 3 Accent Fixtures, a lumen output range of 45lm to 2,000lm can be accomplished. In wattage, this translates to a range from 1W to 33W of LED power. This is all accomplished with no “specialized tool” for brightness adjustment.

BEAM ANGLE

Beam Adjustments range from between 10 degrees to 60 degrees & Zero tools are needed to make these adjustments.

MINI-ACCENT: 10 degrees to 50 degrees

ACCENT: 10 degrees to 60 degrees

GRAND ACCENT: 15 degrees to 60 degrees

FLEXIBILITY/OPTIONS

Multiple OPTIONS for FLEXIBILITY:

Brass or Corrosion Resistant Bronze or Black finishes.

2700K or 3000K (and 4000K in the Grand Accent)

12V or 120V (Accent and Grand Accent)

Long Cowl & Full Cowl options

Suitable for use as an up light or down light

DO YOU HAVE WHAT YOU NEED?

OURS

Just three continuously adjustable lights perfectly illuminate small to giant objects everytime.



Adjustable 10° to 50° beam
Power from 7W to 1W
Dim from 365 lumens to 45 lumens



Adjustable 10° to 60° beam
Power from 16W to 2W
Dim from 1045 lumens to 190 lumens



Adjustable 15° to 60° beam
Power from 33W to 15W
Dim from 2000 lumens to 740 lumens


Others are only available as low as 100 lumens, which may still be too bright for certain applications at night

Covers most commonly needed accent lighting applications

No other landscape accent light offers over 1000 lumens

OTHERS

Each light needs to be ordered specifically for fixed beam angles and set brightness levels.




It's All About the DETAILS

Gone are the appearance of LED diodes. Enjoy the light, without the many glary dots. Quality LED Illumination comparable to incandescent without the pain of a high electricity bill. Light output ranges adjust comparably to anywhere from 10W to 75W MR16 Halogen fixtures.



Continuously Adjustable Brightness Control



Easy Adjustability

No special tools are required to make any adjustments. Twist the collar to change beam angle. Use a flat- or philips-head screw driver to adjust brightness and lock aiming direction.

Materials That Mean Business

Unlike other brands of landscape lighting, we fabricate each product ourselves to a component level. Using the best UV and corrosion resistant materials available to be able to confidently support a true 10 year warranty.

Marine Grade Diecast Stainless Steel
Bronze Stainless Steel

Corrosion Resistant Diecast Aluminum
Bronze on Aluminum
Black on Aluminum

Bronze on Brass
Natural Brass
Diecast Brass



HARDSCAPE LED LANDSCAPE
NEW WITH DUAL CCT AND INTEGRAL BRIGHTNESS CONTROL



Select Warm White (2700K) or Pure White (3000K) light



6 foot of lead wire located on center fixture for ease of measurements

IP66  1838 listed



Continuously adjustable brightness



Removable stainless steel capstone bracket and rotating mounting clips included

HARDSCAPE LED LANDSCAPE
NEW WITH DUAL CCT AND INTEGRAL BRIGHTNESS CONTROL



HARDSCAPE LED LANDSCAPE

NEW WITH DUAL CCT AND INTEGRAL BRIGHTNESS CONTROL



7181-27/30 18 inches

12V

- Integral brightness control select color temperature option*
- Hardscape easily detaches from capstone bracket after installation
- Corrosion-resistant aluminum alloy
- Factory-sealed water tight fixture
- Transformer required (sold separately)
- Tightly spaced and diffused LEDs for even illumination
- Direct burial gel-filled wire nuts included



7121-27/30 12 inches




7061-27/30 6 inches



7031* 3 inches

* Due to its compact size, the 7031 is dedicated in either 2700K or 3000K. Lead wire remains on the side of the fixture.

Input: 9-15VAC
 Lumens: Up to 330 lm
 CRI: 90+
 Rated Life: 50,000 hours



7061, 7121, 7181

7031*

See photometric data on page 102



Length	Model	Color Temp	Wattage	Max Lumens	Finishes
3" *	7031-27 7031-30	2700K Warm White* 3000K Pure White*	1.4W, 2.5VA	40	BZ Bronze on Aluminum GH Graphite SD Sand
6"	7061-27/30	2700K Warm White 3000K Pure White	4.5W, 5.6VA	120	BZ Bronze on Aluminum BBR Bronze on Brass GH Graphite SD Sand
12"	7121-27/30	2700K Warm White 3000K Pure White	7.0W, 7.3VA	225	BZ Bronze on Aluminum BBR Bronze on Brass GH Graphite SD Sand
18"	7181-27/30	2700K Warm White 3000K Pure White	8.5W, 8.5VA	330	BZ Bronze on Aluminum GH Graphite SD Sand

Example: **7181-27/30SD**

GRAND ACCENT LED LANDSCAPE

NEW

MOONLIGHTING EFFECT

Introducing the first landscape accent lights to deliver up to 2000 lumens of light output. When mounted high in trees and pointing downward, Grand Accent creates a beautiful moonlighting effect with a cool white light and superior lumen output.

- New 4000K color temperature option resembles moonlight
- Adjustable beam 15° to 60°
- Continuously adjustable lumen output 740–2000 lm
- Integral brightness control
- One fixture replaces 50W to 100W halogen accent light

GRAND ACCENT LED LANDSCAPE

NEW



1838 listed
1598 listed

12V

Input 9-15VAC
Power 15W to 33W / 21VA -44VA
Brightness 740 lm to 2000 lm
Beam Angle 15° to 60°
CRI 85
Rated Life 45,000 hours

2700K Warm White

5211-27
BK Black on Aluminum
BZ Bronze on Aluminum
BBR Bronze on Brass

3000K Pure White

5211-30
BK Black on Aluminum
BZ Bronze on Aluminum
BBR Bronze on Brass

4000K Pure White

5211-40
BK Black on Aluminum
BZ Bronze on Aluminum
BBR Bronze on Brass

120V

Input 9-15VAC
Power 13W to 31W / 23VA -48VA
Brightness 780 lm to 2050 lm
Beam Angle 15° to 60°
CRI 85
Rated Life 45,000 hours

3000K Pure White


5212-30
BK Black on Aluminum
BZ Bronze on Aluminum
BBR Bronze on Brass

4000K Pure White

5212-40
BK Black on Aluminum
BZ Bronze on Aluminum
BBR Bronze on Brass



See photometric data on pages 95-96



Accessories

5" Long Shroud		5211-LSHR-BK 5211-LSHR-BZ 5211-LSHR-BBR	Black on Aluminum Bronze on Aluminum Bronze on Brass	Reduce glare; ideal for downlighting application	
Grand Accent Snoot		5211-SNOOT-BK 5211-SNOOT-BZ 5211-SNOOT-BBR	Black on Aluminum Bronze on Aluminum Bronze on Brass	Reduce glare; ideal for downlighting application	
9" Mounting Stake		9000-ST9-BZ	Bronze	Durable PC stake	
14" Mounting Stake		9000-ST14-BZ New!	Bronze	Durable PC stake	
Power Stake		M6000-STAKE	Black	Easy wiring accessory designed for 120V products; eliminates the need for a separate J-box.	
Surface Mount Flange/Stake		5000-SCP-BK 5000-SCP-BZ 5000-SCP-BBR	Black on Aluminum Bronze on Aluminum Bronze on Brass	Includes three 7 inch threaded stainless steel stabilizing pins for ground mounting or surface mounts with four screws or over a junction box	
Guardian Mount		9000-SP9-BZ	Stainless Steel	Heavy duty stainless steel spike to position fixture Formed from a single piece of metal	
Gutter Mount Bracket		5000-GM-BK 5000-GM-BZ	Black on Aluminum Bronze on Aluminum	Stainless steel universal mounting bracket for gutter mounting fixture	
Tree Mount Junction Box		5000-TCP-BK 5000-TCP-BZ	Black on Aluminum Bronze on Aluminum	Aluminum box with stainless steel mounting screws; two 2" NPT threaded holes	
		5000-TCL-BK New! 5000-TCL-BZ New!	Black on Aluminum Bronze on Aluminum	Large Aluminum box with stainless steel mounting screws; two 2" NPT threaded holes	
Large Tree Mount Canopy Strap		5000-TST-BK New!	Black on Steel and terylene	Ratcheting device with strap to be used with Large Tree Mount Junction Box (5000-TCL)	
Optics		LENS-25-AMB LENS-25-GRN LENS-25-RED	Amber Green Red	LENS-25-BLU Blue LENS-25-FR Frosted LENS-25-SPR Spread	LENS-25-BEL Beam Elongating Enhances saturation of florals and foliage

Mounting stake (12V), Detachable shroud, 6' lead wire and direct burial gel filled wire nuts (12V) or standard wire nuts (120V) included


ACCENT LED LANDSCAPE

- Continuously Adjustable Brightness Control
Indexed at 2W, 4W, 8W, 13W, 16W

- Continuously Adjustable Beam Angles
Indexed at 10°, 25°, 40°, 60°



ACCENT LED LANDSCAPE

IP66 
1838 listed
1598 listed

12V

- Integral brightness control
- Adjustable beam angle 10° to 60°
- One fixture replaces all older halogen landscape accent lights.

Transformer Required (order separately)

Input Power	9-15VAC
Brightness	2W to 16W / 2VA -23VA
Beam Angle	190 lm to 1045 lm
CRI	10° to 60°
Rated Life	85
	70,000 hours












2700K Warm White

5011-27	BK Black on Aluminum
	BZ Bronze on Aluminum
	BBR Bronze on Brass

3000K Pure White

5011-30	BK Black on Aluminum
	BZ Bronze on Aluminum
	BBR Bronze on Brass

Accessories

6" Long Shroud		5010-LSHR-BK 5010-LSHR-BZ 5010-LSHR-BBR	Black on Aluminum Bronze on Aluminum Bronze on Brass	Reduce glare; ideal for downlighting application
Accent Snoot		5010-SNOOT-BK 5010-SNOOT-BZ 5010-SNOOT-BBR	Black on Aluminum Bronze on Aluminum Bronze on Brass	Reduce glare; ideal for downlighting application
9" Mounting Stake		9000-ST9-BZ	Bronze	Durable PC stake
14" Mounting Stake		9000-ST14-BZ New!	Bronze	Durable PC stake
Power Stake		M6000-STAKE	Black	Easy wiring accessory designed for 120V products; eliminates the need for a separate J-box.
Surface Mount Flange/Stake		5000-SCP-BK 5000-SCP-BZ 5000-SCP-BBR	Black on Aluminum Bronze on Aluminum Bronze on Brass	Includes three 7 inch threaded stainless steel stabilizing pins for ground mounting or surface mounts with four screws or over a junction box
Guardian Mount		9000-SP9-BZ	Stainless Steel	Heavy duty stainless steel spike to position fixture; formed from a single piece of metal
Gutter Mount Bracket		5000-GM-BK 5000-GM-BZ	Black on Aluminum Bronze on Aluminum	Stainless steel universal mounting bracket for gutter mounting fixture
Tree Mount Junction Box		5000-TCP-BK 5000-TCP-BZ	Black on Aluminum Bronze on Aluminum	Aluminum box with stainless steel mounting screws; two 2" NPT threaded holes
		5000-TCL-BK New! 5000-TCL-BZ New!	Black on Aluminum Bronze on Aluminum	Large Aluminum box with stainless steel mounting screws; two 2" NPT threaded holes
Large Tree Mount Canopy Strap		5000-TST-BK New!	Black on Steel and terylene	Ratcheting device with strap to be used with Large Tree Mount Junction Box (5000-TCL)
Optics		LENS-20-AMB Amber LENS-20-GRN Green LENS-20-RED Red	LENS-20-BLU Blue LENS-20-FR Frosted LENS-20-SPR Spread	LENS-20-BEL Beam Elongating Enhances saturation of florals and foliage

Mounting stake (12V), Detachable shroud, 6' lead wire and direct burial gel filled wire nuts (12V) or standard wire nuts (120V) included

120V

- Integral brightness control
- Adjustable beam angle 15° to 60°
- Simple to retrofit existing line voltage systems or coordinate well with a new commercial landscape job

Input Power	110V - 120VAC
Brightness	3.5W to 14.5W
Beam Angle	100 lm to 900 lm
CRI	15° to 60°
Rated Life	85
	45,000 hours


3000K Pure White

5012-30	BK Black on Aluminum
	BZ Bronze on Aluminum
	BBR Bronze on Brass

ilumenight™ color changing accent lights
See pages 25-26



See photometric data on pages 97-98



MINI ACCENT LED LANDSCAPE

- Adjustable beam angle
- IP66 rated, protected against high-pressure water jets
- Includes a detachable shroud
- Solid diecast brass or corrosion resistant aluminum
- Factory sealed water tight fixtures
- Constant output for 9V-15V input
- Can be used as an uplight or downlight
- 2700K or 3000K color temperature



- Continuously Adjustable Brightness Control
Indexed at 1W, 2W, 4W, 6W, 7W

- Continuously Adjustable Beam Angles
Indexed at 10°, 25°, 40°, 50°

MINI ACCENT LED LANDSCAPE



12V

- Integral brightness control
- Adjustable beam angle 10° to 50°
- One fixture replaces all older halogen landscape accent light.

Transformer Required (order separately)

Input	9-15VAC
Power	1W to 7W / 2VA -10.5VA
Brightness	45 lm to 365 lm
Beam Angle	10° to 50°
CRI	85
Rated Life	70,000 hours



Shown with gutter mount bracket accessory



Continuously adjustable brightness control

2700K

Warm White

5111-27

- BK** Black on Aluminum
- BZ** Bronze on Aluminum
- BBR** Bronze on Brass


3000K

Pure White

5111-30

- BK** Black on Aluminum
- BZ** Bronze on Aluminum
- BBR** Bronze on Brass

See photometric data on page 99



Single and Double stem mount available. See pages 17-18

Accessories

5" Long Shroud		5111-LSHR-BK 5111-LSHR-BZ 5111-LSHR-BBR	Black on Aluminum Bronze on Aluminum Bronze on Brass	Reduce glare; ideal for downlighting application	
Mini Accent Snoot		5111-SNOOT-BK 5111-SNOOT-BZ 5111-SNOOT-BBR	Black on Aluminum Bronze on Aluminum Bronze on Brass	Reduce glare; ideal for downlighting application	
9" Mounting Stake		9000-ST9-BZ	Bronze	Durable PC stake	
14" Mounting Stake		9000-ST14-BZ New!	Bronze	Durable PC stake	
Power Stake		M6000-STAKE	Black	Easy wiring accessory designed for 120V products; eliminates the need for a separate J-box.	
Guardian Mount		9000-SP9-BZ	Stainless Steel	Heavy duty stainless steel spike to position fixture; formed from a single piece of metal	
Gutter Mount Bracket		5000-GM-BK 5000-GM-BZ	Black on Aluminum Bronze on Aluminum	Stainless steel universal mounting bracket for gutter mounting fixture	
Tree Mount Junction Box		5000-TCP-BK 5000-TCP-BZ	Black on Aluminum Bronze on Aluminum	Aluminum box with stainless steel mounting screws; two 2" NPT threaded holes	
		5000-TCL-BK New! 5000-TCL-BZ New!	Black on Aluminum Bronze on Aluminum	Large Aluminum box with stainless steel mounting screws; two 2" NPT threaded holes	
Large Tree Mount Canopy Strap		5000-TST-BK New!	Black on Steel and terylene	Ratcheting device with strap to be used with Large Tree Mount Junction Box (5000-TCL)	
Optics		LENS-16-AMB	Amber	LENS-16-BLU Blue LENS-16-FR Frosted LENS-16-SPR Spread LENS-16-BEL Beam Elongating	Enhances saturation of florals and foliage
		LENS-16-GRN	Green		
		LENS-16-RED	Red		

Mounting stake (12V), detachable shroud, 6' lead wire and direct burial gel filled wire nuts (12V) included

MINI ACCENT LED PATH

- IP66 rated, protected against high-pressure water jets
- Factory sealed water tight fixtures
- Constant output for 9V-15V input



MINI ACCENT LED PATH



- Includes 6", 12" and 24" extensions
- IP66 rated, protected against high-pressure water jets
- 10°-50° beam adjustability
- Continuously adjustable beam angles and brightness control
- Detachable shroud
- Constant output for 9V-15V input

SINGLE

Input	9-15VAC
Power	1W to 7W/2VA-10.5VA
Brightness	45lm to 365
Color Temp	2700 & 3000k
CRI	85
Rated Life	70,000 hours

2700 & 3000K Warm and Pure White


Single	BK	Black on Aluminum
6111-27	BZ	Bronze on Aluminum
6111-30	BBR	Bronze on Brass

2700 & 3000K Warm and Pure White

Double	BK	Black on Aluminum
6211-27	BZ	Bronze on Aluminum
6211-30	BBR	Bronze on Brass


DOUBLE

Input	9-15VAC
Power	1W to 7W/2VA-10.5VA x2
Brightness	45lm to 365 x2
Color Temp	2700 & 3000k
CRI	85
Rated Life	70,000 hours



Example: 6111-30BBR

Guardian mount, 6 foot lead wire, and direct burial gel filled wire nuts included



Accessories

5" Long Shroud		5111-LSHR-BK 5111-LSHR-BZ 5111-LSHR-BBR	Black on Aluminum Bronze on Aluminum Bronze on Brass	Reduce glare; ideal for downlighting application
14" Mounting Stake		9000-ST14-BZ New!	Bronze	Durable PC stake
Surface Mount Flange/Stake		5000-SCP-BK 5000-SCP-BZ 5000-SCP-BBR	Black on Aluminum Bronze on Aluminum Bronze on Brass	Includes three 7 inch threaded stainless steel stabilizing pins for ground mounting or surface mounts with four screws or over a junction box
Guardian Mount		9000-SP9-BZ	Stainless Steel	Heavy duty stainless steel spike to position fixture; formed from a single piece of metal

MINI WALL WASH LED LANDSCAPE

WITH DUAL CCT AND INTEGRAL BRIGHTNESS CONTROL

- Select color temperature option
- IP66 rated, protected against powerful water jets
- Solid diecast brass or corrosion resistant aluminum alloy

MINI WALL WASH LED LANDSCAPE WITH DUAL CCT AND INTEGRAL BRIGHTNESS CONTROL



12V

- Transformer required (sold separately)
- Integral brightness control. Select color temperature option
- Mounting stake and direct burial gel-filled wire nuts all included


Input: 9-15VAC
 Power: 1W to 8W / 2-12VA
 Lumens: 80 lm to 420 lm
 Beam Angle: Symmetrical (70° by 95°)
 CRI: 85+
 Rated Life: 60,000 hours
 CCT: 2700K & 3000K
 Warm White & Pure White



See photometric data on page 103

2700 & 3000K Warm and Pure White

5121-27/30
BK Black on Aluminum
BZ Bronze on Aluminum
BBR Bronze on Brass



A uniform wide distribution wall wash
from a small form factor

Accessories

9" Mounting Stake		9000-ST9-BZ	Bronze	Durable PC stake				
14" Mounting Stake		9000-ST14-BZ	New! Bronze	Durable PC stake				
Surface Mount Flange/Stake		5000-SCP-BK 5000-SCP-BZ 5000-SCP-BBR	Black on Aluminum Bronze on Aluminum Bronze on Brass	Includes three 7 inch threaded stainless steel stabilizing pins for ground mounting or surface mounts with four screws or over a junction box				
Guardian Mount		9000-SP9-BZ	Stainless Steel	Heavy duty stainless steel spike to position fixture; formed from a single piece of metal				
Gutter Mount Bracket		5000-GM-BK 5000-GM-BZ	Black on Aluminum Bronze on Aluminum	Stainless steel universal mounting bracket for gutter mounting fixture				
Tree Mount Junction Box		5000-TCP-BK 5000-TCP-BZ	Black on Aluminum Bronze on Aluminum	Aluminum box with stainless steel mounting screws; two 2" NPT threaded holes				
		5000-TCL-BK 5000-TCL-BZ	New! Black on Aluminum New! Bronze on Aluminum	Large Aluminum box with stainless steel mounting screws; two 2" NPT threaded holes				
Large Tree Mount Canopy Strap		5000-TST-BK	New! Black on Steel and terylene	Ratcheting device with strap to be used with Large Tree Mount Junction Box (5000-TCL)				
Optics		LENS-2X3-AMB LENS-2X3-GRN LENS-2X3-RED	Amber Green Red	LENS-2X3-BLU LENS-2X3-FR LENS-2X3-SPR	Blue Frosted Spread	LENS-2X3-BEL	Beam Elongating	Enhances saturation of florals and foliage


WALL WASH LED LANDSCAPE

- A uniform wide distribution wall wash from a small form factor
- IP66 rated, protected against powerful water jets
- Solid diecast brass or corrosion resistant aluminum alloy
- Factory sealed water tight fixtures
- Constant output for 9V-15V, 110V - 120V inputs

- Patent Pending Optical Design
- Even Coverage at 15° Upwards, 50° x 80°

- Continuously Adjustable Brightness Control
Indexed at 2W, 4W, 8W, 13W, 16W

WALL WASH LED LANDSCAPE



12V

- Integral brightness control

Input	9 -15VAC
Power	2W to 16W / 2 - 23VA
Brightness	190 lm to 980 lm
Beam Angle	15° upward (50° by 80°)
CRI	85
Rated Life	70,000 hours

2700K *Warm White*

5021-27	BK Black on Aluminum
	BZ Bronze on Aluminum
	BBR Bronze on Brass

3000K *Pure White*

5021-30	BK Black on Aluminum
	BZ Bronze on Aluminum
	BBR Bronze on Brass

Transformer Required (order separately)

120V

- Integral brightness control

Input	110V - 120VAC
Power	3.5W to 14.5W
Brightness	95 lm to 855 lm
Beam Angle	15° upward (50° by 80°)
CRI	85
Rated Life	45,000 hours


3000K *Pure White*

5022-30	BK Black on Aluminum
	BZ Bronze on Aluminum
	BBR Bronze on Brass

ilumenight™ *color changing accent lights*
 See pages 25-26



See photometric data on page 103



Accessories

9" Mounting Stake		9000-ST9-BZ	Bronze	Durable PC stake
14" Mounting Stake		9000-ST14-BZ New!	Bronze	Durable PC stake
Power Stake		M6000-STAKE	Black	Easy wiring accessory designed for 120V products; eliminates the need for a separate J-box.
Surface Mount Flange/Stake		5000-SCP-BK 5000-SCP-BZ 5000-SCP-BBR	Black on Aluminum Bronze on Aluminum Bronze on Brass	Includes three 7 inch threaded stainless steel stabilizing pins for ground mounting or surface mounts with four screws or over a junction box
Guardian Mount		9000-SP9-BZ	Stainless Steel	Heavy duty stainless steel spike to position fixture; formed from a single piece of metal
Gutter Mount Bracket		5000-GM-BZ 5000-GM-BK	Stainless Steel Black on Aluminum	Stainless steel universal mounting bracket for gutter mounting fixture
Tree Mount Junction Box		5000-TCP-BK 5000-TCP-BZ	Black on Aluminum Bronze on Aluminum	Aluminum box with Stainless steel mounting screws; two 2" NPT threaded holes
Extension Rods		5000-X04-BZ/BK 4 in 5000-X08-BZ/BK 8 in 5000-X12-BZ/BK 12 in	5000-X18-BZ/BK 18 in 5000-X24-BZ/BK 24 in	Extends distance between Accent light and surface mount canopy, stake, or tree mount box
Rod L-Coupler		5000-LCO-BK 5000-LCO-BZ	Black Bronze	
Wall Wash Optics		LENS-2X4-AMB Amber LENS-2X4-GRN Green LENS-2X4-RED Red	LENS-2X4-BLU Blue LENS-2X4-FR Frosted LENS-2X4-SPR Spread	Enhances saturation of florals and foliage and turtle friendly


Mounting stake (12V), detachable shroud, 6' lead wire and direct burial gel filled wire nuts (12V) or standard wire nuts (120V) included

3" INGROUND LED LANDSCAPE

- Tilt and adjust beam angles
- Integral brightness control
- IP67 rated, protected from temporary immersion under water
- Drive over up to 4500lbs
- Solid diecast brass or corrosion resistant cast aluminum
- Available concrete pour kit
- Constant output for 9V-15V or 110V-120V inputs



3" Inground Features




Typical Inground

Most light output goes into the air, causing light pollution




Adjust Beam Angles

Presets at 15°, 30°, 45°, 60°



Adjustable WAC Inground

Adjust the light to where you need it




Typical Inground

Most light output goes into the air, causing light pollution




Tilt and Aim

Up to 40° of adjustability preset at -20°, -10°, 0°, 10°, 20°



Adjustable WAC Inground

Adjust the light to where you need it



Control Brightness

Adjustable from 70 lm to 505 lm
Presets Comparable to
10W, 25W, 35W, 50W, 75W Halogen source



3" INGROUND LED LANDSCAPE



3" INGROUND LED LANDSCAPE

IP67 
 1838 listed
 1598 listed

12V

- Integral brightness control
- Adjustable beam angle
- Directional aim with +/- 20° Tilt

Input 9-15VAC
 Power 2W to 12W / 2-17VA
 Brightness 70 lm to 505 lm
 Beam Angle 15° to 60°
 CRI 85
 Rated Life 55,000 hours

2700K *Warm White*
5031-27
BZ Bronze on Aluminum
BBR Bronze on Brass

3000K *Pure White*
5031-30
BZ Bronze on Aluminum
BBR Bronze on Brass

120V

- Integral brightness control
- Adjustable beam angle



Input 110V - 120VAC
 Power 3W to 11.5W
 Brightness 65 lm to 515 lm
 Beam Angle 15° to 60°
 CRI 85
 Rated Life 45,000 hours

3000K *Pure White*
5032-30
BZ Bronze on Aluminum
BBR Bronze on Brass




ilumenight™ *color changing accent lights*
 *See pages 25-26*



See photometric data on pages 100-101



Accessories


Rock Guard		5030-GRD-BZ 5030-GRD-BBR	Bronze on Aluminum Bronze on Brass	Protects the fixture surface
Optics		LENS-25-AMB LENS-25-GRN LENS-25-RED LENS-25-BLU LENS-25-FR LENS-25-HCL	Amber Green Red Blue Frosted Honeycomb Louver reduces glare	Enhances saturation of florals and foliage
Concrete Pour Kit		5030-PIP-PVC	Shown with temporary dense foam cap	For installation in concrete; five 2" NPT threaded holes, PC

Mounting stake (12V), Detachable shroud, 6' lead wire and direct burial gel filled wire nuts (12V) or standard wire nuts (120V) included

- Color changing
- App-controlled brightness
- IP66 rated (Accent, Wall Wash), IP67 rated (Inground)
- Solid die-cast brass
- Factory sealed water tight fixtures
- 6' lead wire
- Constant output for 9V-15V input

ACCENT 12V COLOR CHANGING

Color and brightness controlled with ilumenight™ mobile app



Input 9-15VAC
 Power 0.5W to 14.5W / 1VA to 17VA
 Brightness Up to 355 lm
 Beam Angle 15° to 60°
 CRI 95+
 Rated Life 45,000 hours

IP66


Model	Finishes
5011-CCBRR	Bronze on Brass
5011-CCBZ	Bronze on Aluminum

See page 12 for accessories

Mounting stake (12V), Detachable shroud, 6' lead wire and direct burial get filled wire nuts (12V)

WALL WASH 12V COLOR CHANGING

Color and brightness controlled with ilumenight™ mobile app



Input 9-15VAC
 Power 0.5W to 14.5W / 1VA to 17VA
 Brightness Up to 430 lm
 Beam Angle 15° upward (50° by 80°)
 CRI 95+
 Rated Life 45,000 hours

IP66


Model	Finishes
5021-CCBRR	Bronze on Brass

See page 20 for accessories

Mounting stake (12V), 6' lead wire and direct burial get filled wire nuts (12V)

3" INGROUND 12V COLOR CHANGING

Color and brightness controlled with ilumenight™ mobile app



Input 9-15VAC
 Power 0.5W to 14.5W / 1VA to 17VA
 Brightness Up to 250 lm
 Beam Angle 15° to 60°
 CRI 95+
 Rated Life 45,000 hours

IP67

Model	Finishes
5031-CCBRR	Bronze on Brass

See page 24 for accessories

6' lead wire and direct burial get filled wire nuts (12V)

ilumenight LED LANDSCAPE

MAKE IT COLORFUL

With ilumenight™ you can take your landscape from warm white to pure white to cool white, red to violet and every color in between all with the touch of a finger.

STEP 1 Download free "ilumenight™" app

STEP 2 Setup login

STEP 3 Command all of your ilumenight landscape fixtures at will



UNDERWATER SPOT LED LANDSCAPE



UNDERWATER SPOT LED LANDSCAPE





676 listed



- Machined brass thumb screw
- Cast brass construction
- IP68 rated, suitable for continuous immersion
- Under water in depths up to 3'
- Factory sealed water tight fixtures
- 30' long lead wire
- Limited lifetime warranty

Input	12-15VAC
Power	10W / 11.2VA
Brightness	780 lm
Beam Angle	60°
Color Temp	3000K
CRI	85
Rated Life	50,000 hours

3000K *Pure White*
5511-30 **NB** Natural Brass



Accessories *Submersible luminaires*

<i>Wall Wash Optics</i> 	LENS-20-AMB LENS-20-GRN LENS-20-RED	<i>Amber</i> <i>Green</i> <i>Red</i>	LENS-20-BLU LENS-20-FR LENS-20-SPR	<i>Blue</i> <i>Frosted</i> <i>Spread</i>	<i>Enhances saturation of florals and foliage and turtle friendly</i>
<i>Direct Burial Waterproof Wire Nuts</i> 	9020-WNT-BK	<i>Silicone filled wire nut with gasket (Pack of 20pcs)</i>			

Detachable shroud and direct burial gel filled wire nuts (12V) or standard wire nuts (120V) included

SUBMERSIBLE 2" INGROUND LED LANDSCAPE

- Constant output for 9V-15V input
- 100%-10% dimming - see specification sheet for list of tested dimmers
- May be used in conjunction with all WAC Landscape Lighting products
- Includes a detachable stainless steel mounting bracket for use in or out of water

SUBMERSIBLE 2" INGROUND LED LANDSCAPE




676 listed

- Solid stainless steel construction
- IP68 rated, suitable for continuous immersion under water
- Factory sealed water tight fixtures
- 30' long lead wire

Input	9-15VAC
Power	4.1W / 6.6VA
Brightness	245 lm
Beam Angle	25°
Color Temp	3000K
CRI	85
Rated Life	70,000 hours

3000K *Pure White*

2031-30 **SS** Stainless Steel



Included stainless steel easy mount accessory for use with underwater applications and above ground on any surface

Designed for underwater or wet application.
30ft long lead wire

RECESSED INGROUNDS + INDICATOR LED LANDSCAPE



- IP68 rated, suitable for continuous immersion under water
- Factory sealed water tight fixtures
- Solid stainless steel construction
- Options for use in outdoor downlight applications
- Constant output for 9V-15V input
- 100%-10% dimming - see specification sheet for list of tested dimmers
- Available concrete pour kit with 18" PVC pipe which can be field shortened

RECESSED INGROUNDS + INDICATOR LED LANDSCAPE



2" APERTURE

Input	9-15VAC	CRI	85
Power	4.1W / 6.6VA	Beam Angle	25°
Brightness	Up to 245 lm	Rated Life	70,000 hours
Color Temp	2700, 3000K		



2" Slim Round

2011-27 | **BS** *Bronzed Stainless Steel*
2011-30 | **SS** *Stainless Steel*



2" Slim Round

2021-27 | **BS** *Bronzed Stainless Steel*
2021-30 | **SS** *Stainless Steel*



2" Square

2051-27 | **BS** *Bronzed Stainless Steel*
2051-30 | **SS** *Stainless Steel*

Slim Round with Honeycomb Louver



2012-27 | **BS** *Bronzed Stainless Steel*
2012-30 | **SS** *Stainless Steel*

Slim Round with Honeycomb Louver


2022-27 | **BS** *Bronzed Stainless Steel*
2022-30 | **SS** *Stainless Steel*

2" Square with Honeycomb Louver

2052-27 | **BS** *Bronzed Stainless Steel*
2052-30 | **SS** *Stainless Steel*



Optional spring clip accessory included



Optional spring clip accessory included



2000-CON-PVC
 2" Concrete Pour Kit

For installation in concrete. Use with a 4" outdoor rated junction box and 18" PVC pipe included.


1" APERTURE

Input	9-15VAC	CRI	85
Power	1.9W 3VA	Beam Angle	50°
Brightness	80 lm	Rated Life	70,000 hours
Color Temp	2700 & 3000K		




1" Slim Round

1011-27 | **SS** *Stainless Steel*
1011-30 | **SS** *Stainless Steel*



1" Round

1021-27 | **SS** *Stainless Steel*
1021-30 | **SS** *Stainless Steel*




Optional spring clip accessory included



1" Square

1051-27 | **SS** *Stainless Steel*
1051-30 | **SS** *Stainless Steel*



Optional spring clip accessory included



1000-CON-PVC
 1" Concrete Pour Kit

For installation in concrete. Use with a 4" outdoor rated junction box and 18" PVC pipe included.

2" RECESSED INGROUNDS + INDICATOR LED LANDSCAPE



- IP68 rated, suitable for continuous immersion under water
- Factory sealed water tight fixtures
- Solid stainless steel construction
- Constant output for 9V-15V input
- 10%-100% dimming - see specification sheet for list of tested dimmers
- Available concrete pour kit with 18" PVC pipe which can be field shortened

RECESSED INGROUNDS + INDICATOR LED LANDSCAPE

IP68



1838 listed

2" APERTURE

Input	9-15VAC	Color Temp	2700K, 3000K
Power	4.1W / 6.6VA	CRI	85
Brightness	Up to 30 lm	Rated Life	70,000 hours





2" QUAD-DIRECTIONAL New!

2" SINGLE DIRECTION

2101-27	BS	<i>Bronzed Stainless Steel</i>
2101-30	SS	<i>Stainless Steel</i>

2091-27	BS	<i>Bronzed Stainless Steel</i>
2091-30	SS	<i>Stainless Steel</i>



Optional spring clip accessory included
6" Lead Wire included

Optional spring clip accessory included
6" Lead Wire included





2" BI-DIRECTIONAL

2" GROUND HOOD

Beam Angle: *Asymmetrical*


2071-27	BS	<i>Bronzed Stainless Steel</i>
2071-30	SS	<i>Stainless Steel</i>

2081-27	BS	<i>Bronzed Stainless Steel</i>
2081-30	SS	<i>Stainless Steel</i>



Optional spring clip accessory included
6" Lead Wire included

Optional spring clip accessory included
6" Lead Wire included



2000-CON-PVC For installation in concrete. Use with a 4" outdoor rated junction box and 2" Concrete Pour Kit 18" PVC pipe included.

12V OUTDOOR SUBMERSIBLE LANDSCAPE TAPE LIGHTING



- Submersible up to 5 feet
- May be tied into any 12V landscape lighting system
- Maximum of 40 ft per run to stay within 5 amps
- Flexible linear lights may be cut to desired length at the end of the run
- Various lengths may be joined together with IP68 rated connectors
- UV-stabilized silicone seals and protects the tape sections

12V OUTDOOR SUBMERSIBLE LANDSCAPE TAPE LIGHTING



- Integrates with other landscape lighting products using the same transformer

Input	12VAC
Power	2W/ 2.1VA <i>per foot</i>
Brightness	Up to 115 lm <i>per foot</i>
CRI	85
Rated Life	60,000 hours




Model	Color Temp	Brightness
8011 1 foot	27BK 2700K Warm White	110 lm per foot
8051 5 feet		
8101 10 feet		
	30BK 3000K Pure White	115 lm per foot



Example: **8051-30BK**

Distinct mechanical and electrical connections minimize spacing between LEDs when joining sections, and allow for seemingly endless tape runs that can be powered separately



IP68 rated for submersion up to 5ft

Accessories

Clear Channel		LED-TO24-CH5	5 feet Includes mounting hardware	Lead Wire with 5A fuse		8000-06BK 6 feet 8000-10BK 10 feet	40 ft max tape run; protects tape sections from over current
End Cap		LED-TO24-EC		Joiner Cable - Short		8001-6BK 6 inch 8001-12BK 1 foot	
Surface Mounting Clip		LED-TO24-C1	Secures on both edges (10 Qty)	Joiner Cable - Long		8001-72BK 6 feet 8001-120BK 10 feet	
Edge Mounting Clip		LED-TO24-C2	Secures on one edge (10 Qty)	4 Way "X" Connector		8003-BK	
Invisible Clip		LED-TO24-C3	Spring clip secures beneath tape (10 Qty)	3 Way "Y" Connector		8002-BK	

DECK & PATIO LED LANDSCAPE

- IP66 rated, protected against powerful water jets
- Translucent lens provides for uniform diffused light output
- 100%-10% dimming - see specification for list of tested dimmers
- Solid diecast brass or corrosion resistant aluminum alloy
- ADA compliant






3011

Input	9-15VAC
Power	2.8W / 4.6VA
Brightness	60 lm
Color Temp	2700 & 3000K
CRI	90+
Rated Life	50,000 hours

2700K & 3000K Warm White & Pure White

3011-27	BK Black on Aluminum
3011-30	BBR Bronze on Brass
	BZ Bronze on Aluminum
	WT White on Aluminum

Example: 3011-27BZ




3021

Input	9-15VAC
Power	2.8W / 4.6VA
Brightness	60 lm
Color Temp	2700 & 3000K
CRI	90+
Rated Life	50,000 hours

2700K & 3000K Warm White & Pure White

3021-27	BK Black on Aluminum
3021-30	BBR Bronze on Brass
	BZ Bronze on Aluminum
	WT White on Aluminum

Example: 3021-30BZ




3031

Input	9-15VAC
Power	2.8W / 4.6VA
Brightness	75 lm
Color Temp	2700 & 3000K
CRI	90+
Rated Life	50,000 hours

2700K & 3000K Warm White & Pure White

3031-27	BK Black on Aluminum
3031-30	BBR Bronze on Brass
	BZ Bronze on Aluminum
	WT White on Aluminum


Example: 3031-27BZ



See photometric data for 3011, 3021, 3031 on pages 104-105

STEP LIGHTS LED LANDSCAPE

- Invisible hardware
- IP66 rated, protected against high-pressure water jets
- Constant output for 9V-15V input
- 100%-10% dimming



STEP LIGHTS LED LANDSCAPE




1838 listed (12V)
1598 listed (120V)

CIRCLE AND SQUARE STEP LIGHTS

- Solid stainless steel construction
- Includes a spring clip for wall or step applications
- 6' lead wire

12V


Input	9-15VAC
Power	4.1W / 6.6VA
Brightness	55 lm
Color Temp	2700 & 3000K
CRI	85
Rated Life	70,000 hours



CIRCLE 2041

2700K & 3000K *Warm White & Pure White*

2041-27	BS	<i>Bronzed Stainless Steel</i>
2041-30	SS	<i>Stainless Steel</i>



SQUARE 2061

2700K & 3000K *Warm White & Pure White*

2061-27	BS	<i>Bronzed Stainless Steel</i>
2061-30	SS	<i>Stainless Steel</i>

Example: 2061-30BS

RECTANGLE STEP LIGHTS


- Corrosion resistant aluminum alloy, or cast stainless steel construction

12V

Input	9-15VAC
Power	2W / 3.1VA
Brightness	Up to 38 lm
Color Temp	2700, 3000k & Amber
CRI	90+
Rated Life	60,000 hours

120V


Input	110-120VAC
Power	3.5W
Brightness	Up to 65 lm
Color Temp	3000K
CRI	90+
Rated Life	54,000 hours



12V

2700K, 3000K & Amber *Warm White, Pure White & Amber*

4011-27	BBR*	Bronze on Brass
4011-30		
4011-AM		
120V	BZ	Bronze on Aluminum
WL-LED100-C		
WL-LED100-AM		
	BK	Black on Aluminum
	WT	White on Aluminum
	SS*	Cast Stainless Steel



12V

2700K, 3000K & Amber *Warm White, Pure White & Amber*

4021-27	BZ	Bronze on Aluminum
4021-30		
4021-AM		
120V	BK	Black on Aluminum
WL-LED200-C		
WL-LED200-AM		
	WT	White on Aluminum
	SS*	Cast Stainless Steel

Example: WL-LED200-C-BK

*Cast Stainless Steel finish is only available in 3000K and Amber colors.

**Available in 277V; Example: WL-LED100F-C-WT; BBR finish is not available in 277V option



12V & 120V RECTANGULAR STEP & WALL LIGHTS

LED LANDSCAPE



Input:	12V	120V
Brightness:	Up to 4 lm	Up to 4 lm
CRI:	90	90
Dimming:	100% - 10% MLV	100% - 10% ELV
Rated Life:	60,000 hours	50,000 hours

- Fluid decorative profile with full cut-off illumination
- Die-cast aluminum construction with abrasion-resistant powder-coated finish
- Title 24 compliant (120V only)



Voltage	Power	Model	Color Temp	Finishes
12V	2W / 3.1VA	4031-27	2700K	BK Black on AL
		4031-30	3000K	BZ Bronze on AL
		4031-AM	Amber	WT White on AL
120V	3.5W	WL-LED110-C	3000K	BK Black on AL
		WL-LED110-AM	Amber	BZ Bronze on AL
				WT White on AL


Example: **4031-30WT**
Example: **WL-LED110-C-WT**

Voltage	Power	Model	Color Temp	Finishes
12V	2W / 3.1VA	4041-27	2700K	BK Black on AL
		4041-30	3000K	BZ Bronze on AL
		4041-AM	Amber	WT White on AL
120V	3.5W	WL-LED210-C	3000K	BK Black on AL
		WL-LED210-AM	Amber	BZ Bronze on AL
				WT White on AL

Example: **4041-30BK**
Example: **WL-LED210-C-BK**

Input:	12V	120V
Brightness:	Up to 2 lm	Up to 3 lm
CRI:	90	90
Dimming:	100% - 10% MLV	100% - 10% ELV
Rated Life:	60,000 hours	50,000 hours

- Geometric design with downward illumination
- Die-cast aluminum construction with abrasion-resistant powder-coated finish
- Title 24 compliant (120V only)



Voltage	Power	Model	Color Temp	Finishes
12V	2W / 3.1VA	4091-27	2700K	BK Black on AL
		4091-30	3000K	BZ Bronze on AL
		4091-AM	Amber	WT White on AL
120V	3.5W	WL-LED140-C	3000K	BK Black on AL
		WL-LED140-AM	Amber	BZ Bronze on AL
				WT White on AL

Example: **4091-30BK**
Example: **WL-LED140-C-BK**

IP66 rated self contained fixture with various face plates. Fits into a switch box or a 2" x 4" junction box with minimum inside dimensions of 3"L x 2"W x 2.5"D.



AL - Aluminum

12V & 120V RECTANGULAR STEP & WALL LIGHTS

LED LANDSCAPE

Input:	12V	120V
Brightness:	Up to 28 lm	Up to 40 lm
CRI:	90	90
Dimming:	100% - 10% MLV	100% - 10% ELV
Rated Life:	60,000 hours	50,000 hours

- Tempered glass diffuses light for even illumination
- Die-cast aluminum construction with abrasion-resistant powder-coated finish, or marine-grade stainless steel option available
- Title 24 compliant (120V only)





Mounts Vertically or Horizontally

Voltage	Power	Model	Color Temp	Finishes
12V	2W / 3.1VA	4071-27	2700K	BK Black on AL
		4071-30	3000K	BZ Bronze on AL
		4071-AM	Amber	SS Stainless Steel
				WT White on AL
120V	3.5W	WL-LED130-C	3000K	BK Black on AL
		WL-LED130-AM	Amber	BZ Bronze on AL
				SS Stainless Steel
				WT White on AL

Example: **4071-27SS**
Example: **WL-LED130-C-SS**

Input:	12V	120V
Brightness:	Up to 17 lm	Up to 36 lm
CRI:	90	90
Dimming:	100% - 10% MLV	100% - 10% ELV
Rated Life:	60,000 hours	50,000 hours

- Louvered design shields glare for visual comfort
- Die-cast aluminum construction with abrasion-resistant powder-coated finish
- Title 24 compliant (120V only)



Voltage	Power	Model	Color Temp	Finishes
12V	2W / 3.1VA	4051-27	2700K	BK Black on AL
		4051-30	3000K	BZ Bronze on AL
		4051-AM	Amber	WT White on AL
120V	3.5W	WL-LED120-C	3000K	BK Black on AL
		WL-LED120-AM	Amber	BZ Bronze on AL
				WT White on AL

Example: **4051-30BZ**
Example: **WL-LED120-C-BZ**

Voltage	Power	Model	Color Temp	Finishes
12V	2W / 3.1VA	4061-27	2700K	BK Black on AL
		4061-30	3000K	BZ Bronze on AL
		4061-AM	Amber	WT White on AL
120V	3.5W	WL-LED220-C	3000K	BK Black on AL
		WL-LED220-AM	Amber	BZ Bronze on AL
				WT White on AL

Example: **4061-30BZ**
Example: **WL-LED220-C-BZ**

AL - Aluminum

TIKI LED AREA LIGHT

- IP66 rated, protected against high-pressure water jets
- Factory sealed water tight fixtures
- Solid brass or corrosion resistant aluminum alloy
- Constant output for 9V-15V input



TIKI LED AREA LIGHT




- Sturdy side mount design works well in applications where directional illumination is desired
- Recommended spacing for installation:
Residential: 7 to 9ft
Commercial: 5 to 7ft


Input	9-15VAC	
Power	6.5W / 9.5VA	
Brightness	Up to 225 lm	
Color Temp	2700 & 3000K	
CRI	90	
Rated Life	60,000 hours	
2700 & 3000K	<i>Warm and Pure White</i>	
22"	BK	<i>Black on Aluminum</i>
6041-27	BZ	<i>Bronze on Aluminum</i>
6041-30	BBR	<i>Bronze on Brass</i>
15"		
6042-27	BK	<i>Black on Aluminum</i>
6042-30	BZ	<i>Bronze on Aluminum</i>

Example: 6041-30BBR





Mounting stake, 6 foot lead wire, and direct burial gel filled wire nuts included



MINI
TIKI
6042



Accessories

9" Mounting Stake		9000-ST9-BZ	Bronze	Durable PC stake
14" Mounting Stake		9000-ST14-BZ New!	Bronze	Durable PC stake
Surface Mount Flange/Stake		5000-SCP-BK 5000-SCP-BZ 5000-SCP-BBR	Black on Aluminum Bronze on Aluminum Bronze on Brass	Includes three 7 inch threaded stainless steel stabilizing pins for ground mounting or surface mounts with four screws or over a junction box
Guardian Mount		9000-SP9-BZ	Stainless Steel	Heavy duty stainless steel spike to position fixture; formed from a single piece of metal

CANOPY LED AREA LIGHT

- IP66 rated, protected against high-pressure water jets
- Factory sealed water tight fixtures
- Solid brass or corrosion resistant aluminum alloy
- Constant output for 9V-15V input



CANOPY LED AREA LIGHT



- Sturdy side mount design works well in applications where directional illumination is desired
- Recommended spacing for installation:
Residential: 7 to 9ft
Commercial: 5 to 7ft

Input	9-15VAC
Power	6.5W / 9.5VA
Brightness	Up to 225 lm
Color Temp	2700 & 3000K
CRI	90
Rated Life	60,000 hours



2700 & 3000K Warm and Pure White

6051-27	BK	Black on Aluminum
6051-30	BZ	Bronze on Aluminum
	BBR	Bronze on Brass



Example: 6051-30BZ

Mounting stake, 6 foot lead wire, and direct burial gel filled wire nuts included



Accessories

9" Mounting Stake		9000-ST9-BZ	Bronze	Durable PC stake
14" Mounting Stake		9000-ST14-BZ New!	Bronze	Durable PC stake
Surface Mount Flange/Stake		5000-SCP-BK 5000-SCP-BZ 5000-SCP-BBR	Black on Aluminum Bronze on Aluminum Bronze on Brass	Includes three 7 inch threaded stainless steel stabilizing pins for ground mounting or surface mounts with four screws or over a junction box
Guardian Mount		9000-SP9-BZ	Stainless Steel	Heavy duty stainless steel spike to position fixture; formed from a single piece of metal

LEDGE LED PATH

- IP66 rated, protected against high-pressure water jets
- Factory sealed water tight fixtures
- Constant output for 9V-15V input



LEDGE LED PATH



- Sleek linear design blends seamlessly into pathways while providing soft, even illumination
- Recommended spacing for installation:
Residential: 8 to 10ft
Commercial: 5 to 7ft



Input	9-15VAC
Power	3.0W / 4.5VA
Brightness	Up to 105 lm
Color Temp	2700 & 3000K
CRI	90
Rated Life	60,000 hours

3000K *Pure White*





6081-27	BK <i>Black on Aluminum</i>
6081-30	BZ <i>Bronze on Aluminum</i>

Example: 6081-27BZ

Mounting stake, 6 foot lead wire, and direct burial gel filled wire nuts included



Accessories

9" Mounting Stake		9000-ST9-BZ	Bronze	Durable PC stake
14" Mounting Stake		9000-ST14-BZ New!	Bronze	Durable PC stake
Surface Mount Flange/Stake		5000-SCP-BK 5000-SCP-BZ 5000-SCP-BBR	Black on Aluminum Bronze on Aluminum Bronze on Brass	Includes three 7 inch threaded stainless steel stabilizing pins for ground mounting or surface mounts with four screws or over a junction box
Guardian Mount		9000-SP9-BZ	Stainless Steel	Heavy duty stainless steel spike to position fixture; formed from a single piece of metal

SLIDE LED PATH

- IP66 rated, protected against high-pressure water jets
- Factory sealed water tight fixtures
- Constant output for 9V-15V input



SLIDE LED PATH




- Sleek linear design blends seamlessly into pathways while providing soft, even illumination
- Recommended spacing for installation:
Residential: 9 to 11ft
Commercial: 5 to 7ft

Input 9-15VAC
Power 3.0W / 4.5VA
Brightness Up to 95 lm
Color Temp 3000K
CRI 90
Rated Life 60,000 hours


3000K Pure White

6311- Small
6321- Large **BZ** Bronze on Aluminum

Mounting stake, 6 foot lead wire, and direct burial gel filled wire nuts included





6311







6311 Small
Residential: 7 to 9ft
Commercial: 4 to 6ft

6321 Large
Residential: 9 to 11ft
Commercial: 5 to 7ft



Accessories

9" Mounting Stake		9000-ST9-BZ	Bronze	Durable PC stake
14" Mounting Stake		9000-ST14-BZ New!	Bronze	Durable PC stake
Surface Mount Flange/Stake		5000-SCP-BK 5000-SCP-BZ 5000-SCP-BBR	Black on Aluminum Bronze on Aluminum Bronze on Brass	Includes three 7 inch threaded stainless steel stabilizing pins for ground mounting or surface mounts with four screws or over a junction box
Guardian Mount		9000-SP9-BZ	Stainless Steel	Heavy duty stainless steel spike to position fixture; formed from a single piece of metal

LINEAR LED PATH

- IP66 rated, protected against high-pressure water jets
- Factory sealed water tight fixtures
- Constant output for 9V-15V input



LINEAR LED PATH



- Sleek linear design blends seamlessly into pathways while providing soft, even illumination
- Recommended spacing for installation :
Residential: 7 to 9ft
Commercial: 4 to 6ft



Input	9-15VAC
Power	2.9W / 4.7VA
Brightness	Up to 95 lm
Color Temp	2700 & 3000K
CRI	90
Rated Life	60,000 hours

2700 & 3000K Warm and Pure White





6021-27	BK	Black on Aluminum
6021-30	BZ	Bronze on Aluminum

Example: 6021-30BK

Mounting stake, 6 foot lead wire, and direct burial gel filled wire nuts included



Accessories

9" Mounting Stake		9000-ST9-BZ	Bronze	Durable PC stake
14" Mounting Stake		9000-ST14-BZ New!	Bronze	Durable PC stake
Surface Mount Flange/Stake		5000-SCP-BK 5000-SCP-BZ	Black on Aluminum Bronze on Aluminum	Includes three 7 inch threaded stainless steel stabilizing pins for ground mounting or surface mounts with four screws or over a junction box
Guardian Mount		9000-SP9-BZ	Stainless Steel	Heavy duty stainless steel spike to position fixture; formed from a single piece of metal

BALANCE SINGLE LED PATH

- IP66 rated, protected against high-pressure water jets
- Factory sealed water tight fixtures
- Constant output for 9V-15V input



BALANCE SINGLE LED PATH



- Sleek linear design blends seamlessly into pathways while providing soft, even illumination
- Recommended spacing for installation :
Residential: 11 to 13ft
Commercial: 7 to 9ft



Input	9-15VAC
Power	6.5W / 11.5VA
Brightness	Up to 275 lm
Color Temp	2700 & 3000K
CRI	90
Rated Life	60,000 hours

2700 & 3000K Warm and Pure White





6061-27	BK	Black on Aluminum
6061-30	BZ	Bronze on Aluminum

Example: 6061-30BZ

Mounting stake, 6 foot lead wire, and direct burial gel filled wire nuts included



Accessories

9" Mounting Stake		9000-ST9-BZ	Bronze	Durable PC stake
14" Mounting Stake		9000-ST14-BZ New!	Bronze	Durable PC stake
Surface Mount Flange/Stake		5000-SCP-BK 5000-SCP-BZ	Black on Aluminum Bronze on Aluminum	Includes three 7 inch threaded stainless steel stabilizing pins for ground mounting or surface mounts with four screws or over a junction box
Guardian Mount		9000-SP9-BZ	Stainless Steel	Heavy duty stainless steel spike to position fixture; formed from a single piece of metal

BALANCE DOUBLE LED PATH

- IP66 rated, protected against high-pressure water jets
- Factory sealed water tight fixtures
- Constant output for 9V-15V input



BALANCE DOUBLE LED PATH



- Sleek linear design blends seamlessly into pathways while providing soft, even illumination
- Recommended spacing for installation :
Residential: 11 to 13ft
Commercial: 7 to 9ft



Input	9-15VAC
Power	10W / 14VA
Brightness	Up to 375 lm
Color Temp	2700 & 3000K
CRI	90
Rated Life	60,000 hours

2700 & 3000K Warm and Pure White

6071-27	BK Black on Aluminum
6071-30	BZ Bronze on Aluminum

Example: 6071-30BZ

Mounting stake, 6 foot lead wire, and direct burial gel filled wire nuts included



Accessories

9" Mounting Stake		9000-ST9-BZ	Bronze	Durable PC stake
14" Mounting Stake		9000-ST14-BZ New!	Bronze	Durable PC stake
Surface Mount Flange/Stake		5000-SCP-BK 5000-SCP-BZ	Black on Aluminum Bronze on Aluminum	Includes three 7 inch threaded stainless steel stabilizing pins for ground mounting or surface mounts with four screws or over a junction box
Guardian Mount		9000-SP9-BZ	Stainless Steel	Heavy duty stainless steel spike to position fixture; formed from a single piece of metal

QUAD LED PATH

- IP66 rated, protected against high-pressure water jets
- Factory sealed water tight fixtures
- Constant output for 9V-15V input



QUAD LED PATH



- Sleek linear design blends seamlessly into pathways while providing soft, even illumination
- Recommended spacing for installation :
Residential: 8 to 10ft
Commercial: 5 to 7ft



Input	9-15VAC
Power	3W / 4.5VA
Brightness	Up to 100 lm
Color Temp	2700 & 3000K
CRI	90
Rated Life	60,000 hours

2700 & 3000K Warm and Pure White





6091-27
6091-30 | **BZ** Bronze on Aluminum

Example: 6091-30BZ

Mounting stake, 6 foot lead wire, and direct burial gel filled wire nuts included



Accessories

9" Mounting Stake		9000-ST9-BZ	Bronze	Durable PC stake
14" Mounting Stake		9000-ST14-BZ New!	Bronze	Durable PC stake
Surface Mount Flange/Stake		5000-SCP-BK 5000-SCP-BZ	Black on Aluminum Bronze on Aluminum	Includes three 7 inch threaded stainless steel stabilizing pins for ground mounting or surface mounts with four screws or over a junction box
Guardian Mount		9000-SP9-BZ	Stainless Steel	Heavy duty stainless steel spike to position fixture; formed from a single piece of metal

ECLIPSE LED PATH

- IP66 rated, protected against high-pressure water jets
- Factory sealed water tight fixtures
- Solid diecast corrosion resistant aluminum alloy
- Constant output for 9V-15V input



ECLIPSE LED PATH



- Sturdy side mount design works well in applications where directional illumination is desired
- Recommended spacing for installation :
Residential: 8 to 10ft
Commercial: 5 to 7ft



Input	9-15VAC
Power	2.9W / 4.7VA
Brightness	Up to 125 lm
Color Temp	2700 & 3000K
CRI	90
Rated Life	60,000 hours

2700 & 3000K Warm and Pure White

6031-27	BK	Black on Aluminum
6031-30	BZ	Bronze on Aluminum

Example: 6031-30BZ

Mounting stake, 6 foot lead wire, and direct burial gel filled wire nuts included



Accessories

9" Mounting Stake		9000-ST9-BZ	Bronze	Durable PC stake
14" Mounting Stake		9000-ST14-BZ New!	Bronze	Durable PC stake
Surface Mount Flange/Stake		5000-SCP-BK 5000-SCP-BZ	Black on Aluminum Bronze on Aluminum	Includes three 7 inch threaded stainless steel stabilizing pins for ground mounting or surface mounts with four screws or over a junction box
Guardian Mount		9000-SP9-BZ	Stainless Steel	Heavy duty stainless steel spike to position fixture; formed from a single piece of metal

AREA LED AREA LIGHT

- IP66 rated, protected against high-pressure water jets
- Factory sealed water tight fixtures
- Solid brass or corrosion resistant aluminum alloy
- Constant output for 9V-15V input



AREA LED AREA LIGHT



- Broad appeal makes this fixture suitable for varying landscape designs
- Recommended spacing for installation :
Residential: 11 to 13ft
Commercial: 7 to 9ft



Input	9-15VAC
Power	5.8W / 9.4VA
Brightness	Up to 150 lm
Color Temp	2700 & 3000K
CRI	90
Rated Life	60,000 hours

2700 & 3000K Warm and Pure White





6011-27	BK	Black on Aluminum
6011-30	BZ	Bronze on Aluminum
	BBR	Bronze on Brass

Example: 6011-30BZ

Mounting stake, 6 foot lead wire, and direct burial gel filled wire nuts included



Accessories

9" Mounting Stake		9000-ST9-BZ	Bronze	Durable PC stake
14" Mounting Stake		9000-ST14-BZ New!	Bronze	Durable PC stake
Surface Mount Flange/Stake		5000-SCP-BK 5000-SCP-BZ	Black on Aluminum Bronze on Aluminum	Includes three 7 inch threaded stainless steel stabilizing pins for ground mounting or surface mounts with four screws or over a junction box
Guardian Mount		9000-SP9-BZ	Stainless Steel	Heavy duty stainless steel spike to position fixture; formed from a single piece of metal

GATE LED BOLLARD/PATH



GATE LED BOLLARD/PATH

- IP66 rated, protected against high-pressure water jets
- Factory sealed water tight fixtures
- Constant output for 9V-15V input
- Mounting accessories included
- Detachable back plate for lighting control included



Input	9-15VAC
Power	7.2W, 7.6VA
Brightness	Up to 115 lm
Color Temp	2700 & 3000K
CRI	90
Rated Life	60,000 hours

2700 & 3000K *Warm and Pure White*

6651-27	BK	<i>Black on Aluminum</i>
6651-30	BZ	<i>Bronze on Aluminum</i>

Example: 6651-30BK

Power stake, 6 foot lead wire, and direct burial gel filled wire nuts included



Shown without plate



Shown with plate



Mounting accessory included
12V



M6000-STAKE

- Sleek linear design blends seamlessly into pathways while providing soft, even illumination



Single direction illumination with back plate

SCOOP 12V/120V/277V LED BOLLARD

- IP66 rated, protected against high-pressure water jets
- Factory sealed water tight fixtures
- Constant output for 9V-15V input
- Mounting accessories included



SCOOP 12V/120V/277V LED BOLLARD



1838 listed
1598 listed

12V

Input	9-15VAC
Power	7.8W/8.5VA
Brightness	Up to 180 lm
Color Temp	2700 & 3000K
CRI	90
Rated Life	60,000 hours

2700 & 3000K Warm and Pure White

6611-27	BK Black on Aluminum
6611-30	BZ Bronze on Aluminum

MLV dimming only

120V

Input	120V
Power	12.5W
Brightness	Up to 350 lm
Color Temp	2700 & 3000K
CRI	90
Rated Life	60,000 hours

2700 & 3000K Warm and Pure White

6612-27	BK Black on Aluminum
6612-30	BZ Bronze on Aluminum

TRIAC or ELV dimming

277V

Input	277V
Power	13.2W
Brightness	Up to 370 lm
Color Temp	2700 & 3000K
CRI	90
Rated Life	60,000 hours

2700 & 3000K Warm and Pure White

6613-27	BK Black on Aluminum
6613-30	BZ Bronze on Aluminum


ELV dimming only

Example: 6611-30BK

Recommended spacing for installation :

(12V) 6611


- Residential: 5 to 6ft
- Commercial: 3 to 4ft




Recommended spacing for installation:

(120V, 277V) 6612, 6613


- Residential: 6.5 to 7.5ft
- Commercial: 4.5 to 5.5ft



- Sleek linear design blends seamlessly into pathways while providing soft, even illumination



Mounting accessory included



M6000-STAKE

M6610-CON-KIT




Even illumination front and back

CHAMBER 12V/120V/277V LED BOLLARD

- IP66 rated, protected against high-pressure water jets
- Factory sealed water tight fixtures
- Constant output for 9V-15V input
- Mounting accessories included



CHAMBER 12V/120V/277V LED BOLLARD



12V

Input	9-15VAC
Power	5.8W, 6.2VA
Brightness	Up to 150 lm
Color Temp	2700 & 3000K
CRI	90
Rated Life	60,000 hours

2700 & 3000K Warm and Pure White

6631-27	BK Black on Aluminum
6631-30	BZ Bronze on Aluminum

MLV dimming only

120V

Input	120V
Power	12.5W
Brightness	Up to 400 lm
Color Temp	2700 & 3000K
CRI	90
Rated Life	60,000 hours

2700 & 3000K Warm and Pure White

6632-27	BK Black on Aluminum
6632-30	BZ Bronze on Aluminum

TRIAC or ELV dimming

277V

Input	277V
Power	13.2W
Brightness	Up to 450 lm
Color Temp	2700 & 3000K
CRI	90
Rated Life	60,000 hours

2700 & 3000K Warm and Pure White


6633-27	BK Black on Aluminum
6633-30	BZ Bronze on Aluminum

ELV dimming only

Example: 6633-30BK


Recommended spacing for installation :
(12V) 6631

- Residential: 19.5 to 23ft
- Commercial: 13 to 15.5ft




Recommended spacing for installation :
(120V, 277V) 6632, 6633

- Residential: 12.5 to 15ft
- Commercial: 8 to 10ft



- Sleek linear design blends seamlessly into pathways while providing soft, even illumination



Mounting accessory included

12V

120V/277V



M6000-STAKE


M6630-CON-KIT

TOWER 12V/120V/277V LED BOLLARD

- IP66 rated, protected against high-pressure water jets
- Factory sealed water tight fixtures
- Constant output for 9V-15V input
- Mounting accessories included



TOWER 12V/120V/277V LED BOLLARD



12V

Input	9-15VAC
Power	5.8W, 6.2VA
Brightness	Up to 170 lm
Color Temp	2700 & 3000K
CRI	90
Rated Life	60,000 hours

2700 & 3000K Warm and Pure White

6621-27	BK	Black on Aluminum
6621-30	BZ	Bronze on Aluminum

MLV dimming only

120V

Input	120V
Power	12.5W
Brightness	Up to 430 lm
Color Temp	2700 & 3000K
CRI	90
Rated Life	60,000 hours

2700 & 3000K Warm and Pure White

6622-27	BK	Black on Aluminum
6622-30	BZ	Bronze on Aluminum

TRIAC or ELV dimming

277V

Input	277V
Power	13.2W
Brightness	Up to 470 lm
Color Temp	2700 & 3000K
CRI	90
Rated Life	60,000 hours

2700 & 3000K Warm and Pure White

6623-27	BK	Black on Aluminum
6623-30	BZ	Bronze on Aluminum


ELV dimming only

Example: 6622-30BK

Recommended spacing for installation :

(**12V**) 6621


- Residential: 12 to 14.5ft
- Commercial: 4 to 6.5ft




Recommended spacing for installation :

(**120V, 277V**) 6622, 6623

- Residential: 16 to 22ft
- Commercial: 8 to 11ft



- Sleek linear design blends seamlessly into pathways while providing soft, even illumination



Mounting accessory included

12V

120V/277V



M6000-STAKE


M6620-CON-KIT

PARK 12V/120V/277V LED BOLLARD

- IP66 rated, protected against high-pressure water jets
- Factory sealed water tight fixtures
- Constant output for 9V-15V input
- Mounting accessories included



PARK 12V/120V/277V LED BOLLARD



12V

Input	9-15VAC
Power	5.8W, 6.2VA
Brightness	Up to 195 lm
Color Temp	2700 & 3000K
CRI	90
Rated Life	60,000 hours

2700 & 3000K Warm and Pure White

6641-27	BK Black on Aluminum
6641-30	BZ Bronze on Aluminum

MLV dimming only

120V

Input	120V
Power	12.5W
Brightness	Up to 470 lm
Color Temp	2700 & 3000K
CRI	90
Rated Life	60,000 hours

2700 & 3000K Warm and Pure White

6642-27	BK Black on Aluminum
6642-30	BZ Bronze on Aluminum

TRIAC or ELV dimming

277V

Input	277V
Power	13.2W
Brightness	Up to 550 lm
Color Temp	2700 & 3000K
CRI	90
Rated Life	60,000 hours

2700 & 3000K Warm and Pure White

6643-27	BK Black on Aluminum
6643-30	BZ Bronze on Aluminum


ELV dimming only

Example: 6641-30BK

Recommended spacing for installation :

(12V) 6641


- Residential: 11.5 to 14ft
- Commercial: 7 to 9ft




Recommended spacing for installation :

(120V, 277V) 6642, 6643

- Residential: 12.5 to 14.5ft
- Commercial: 8 to 9.5ft



- Sleek linear design blends seamlessly into pathways while providing soft, even illumination



Mounting accessory included

12V

120V/277V



M6000-STAKE

M6640-CON-KIT

TRANSFORMER LED LANDSCAPE



1838 listed

From our fully adjustable integrated LED accent light to our submersible in-grounds, every product is engineered to work well together as a fully integrated solution. We have everything you need whether you're lighting a small jewel of a garden or a sublime outdoor oasis, all connected to the same transformer.

Model

9075-TRN-SS	75W Max Dimensions: 13.97" L x 5.35" W x 5.63" H
9150-TRN-SS	150W Max Dimensions: 18.90" L x 6.69" W x 6.30" H
9300-TRN-SS	300W Max Dimensions: 18.90" L x 6.69" W x 6.30" H
9600-TRN-SS	600W Max (2 x 300W outputs) Dimensions: 14.49" L x 10.08" W x 5.94" H

- IP65 rated
- 12V to 15V taps
- Knock outs for power and photosensor connections
- 3-prong outlet for timer
- Outdoor rated stainless steel transformer contains an outdoor rated 3-prong plug for power
















Accessories LED LANDSCAPE



Mechanical Timer		9000-MTI-WT	White	Connect within the transformer
Photosensor		9000-PCH-GY	1000VA Max	Attached directly to the transformer
Photosensor - Remote		9000-PCR-GY	1000VA Max	If transformer is located in a shady spot, this photosensor has a 10 foot cord and a stainless steel bracket to secure in a sunny area
Direct Burial Water proof Wire Nuts		9020-WNT-BK		Silicone filled wire nut with gasket (Pack of 20pcs)
12V Direct Burial Outdoor Cable		9100-12G-BK 9250-12G-BK 9500-12G-BK	100 feet 12 gauge 250 feet 12 gauge 500 feet 12 gauge	

ACCESSORIES LED LANDSCAPE

Mounting & Glare Control Accessories LED LANDSCAPE

5" Long Shroud For 5211 Grand Accent		5211-LSHR-BK 5211-LSHR-BZ 5211-LSHR-BBR		Reduce glare; ideal for downlighting application
6" Long Shroud For 5011/5012 Accent		5010-LSHR-BZ 5010-LSHR-BBR 5010-LSHR-BK		Reduce glare; ideal for downlighting application
5" Long Shroud For 5111 Mini Accent		5111-LSHR-BZ 5111-LSHR-BBR 5111-LSHR-BK		Reduce glare; ideal for downlighting application
Grand Accent Snoot		5211-SNOOT-BK 5211-SNOOT-BZ 5211-SNOOT-BBR		Reduce glare; ideal for downlighting application
Accent Snoot		5010-SNOOT-BK 5010-SNOOT-BZ 5010-SNOOT-BBR		Reduce glare; ideal for downlighting application
Mini Accent Snoot		5111-SNOOT-BK 5111-SNOOT-BZ 5111-SNOOT-BBR		Reduce glare; ideal for downlighting application
9" Mounting Stake		9000-ST9-BZ		Durable PC stake
14" Mounting Stake		9000-ST14-BZ	New!	Durable PC stake
Surface Mount Flange/Stake		5000-SCP-BZ 5000-SCP-BBR 5000-SCP-BK		Includes three 7 inch threaded stainless steel stabilizing pins for ground mounting or surface mounts with four screws or over a junction box
Guardian Mount		9000-SP9-BZ		Heavy duty stainless steel spike to position fixture; formed from a single piece of metal
Gutter Mount Bracket		5000-GM-BK 5000-GM-BZ		Stainless steel universal mounting bracket for gutter mounting fixture
Tree Mount Junction Box		5000-TCP-BK 5000-TCP-BZ		Aluminum box with stainless steel mounting screws; two 2" NPT threaded holes
		5000-TCL-BK 5000-TCL-BZ	New! New!	Large aluminum box with stainless steel mounting screws; two 2" NPT threaded holes
Large Tree Mount Canopy Strap		5000-TST-BK	New!	Ratcheting device with strap to be used with Large Tree Mount Junction Box (5000-TCL)

Optic Accessories LED LANDSCAPE

Grand Accent Optics		LENS-25-AMB LENS-25-GRN LENS-25-RED	Amber Green Red	LENS-25-BLU LENS-25-FR LENS-25-SPR	Blue Frosted Spread	LENS-25-BEL	Beam Elongating	Enhances saturation of florals and foliage
Accent Optics		LENS-20-AMB LENS-20-GRN LENS-20-RED	Amber Green Red	LENS-20-BLU LENS-20-FR LENS-20-SPR	Blue Frosted Spread	LENS-20-BEL	Beam Elongating	Enhances saturation of florals and foliage
Mini Accent Optics		LENS-16-AMB LENS-16-GRN LENS-16-RED	Amber Green Red	LENS-16-BLU LENS-16-FR LENS-16-SPR	Blue Frosted Spread	LENS-16-BEL	Beam Elongating	Enhances saturation of florals and foliage
Mini Wall Wash Optics		LENS-2X3-AMB LENS-2X3-GRN LENS-2X3-RED	Amber Green Red	LENS-2X3-BLU LENS-2X3-FR LENS-2X3-SPR	Blue Frosted Spread	LENS-2X3-BEL	Beam Elongating	Enhances saturation of florals and foliage
Wall Wash Optics		LENS-2X4-AMB LENS-2X4-GRN LENS-2X4-RED	Amber Green Red	LENS-2X4-BLU LENS-2X4-FR LENS-2X4-SPR	Blue Frosted Spread	Enhances saturation of florals and foliage and turtle friendly		

LINE VOLTAGE LED LANDSCAPE OFFERING



1598 listed


ACCENT 120V

Integral brightness control, adjustable beam angle



Power 3.5W to 14.5W
 Brightness 100lm to 900lm
 Beam Angle 15° to 60°
 CRI 85
 Color Temp 3000K Pure White
 Rated Life 45,000 hours
 Listing IP-66

Detachable shroud
 6' lead wire and wire nuts included



Model	Finishes
-------	----------

5012-30BK	Black on Aluminum
5012-30BZ	Bronze on Aluminum
5012-30BBR	Bronze on Brass


WALL WASH 120V

Integral brightness control



Power 3.5W to 14.5W
 Brightness 95lm to 855lm
 Beam Angle 15° upward (50° by 80°)
 CRI 85
 Color Temp 3000K Pure White
 Rated Life 45,000 hours
 Listing IP-66

6' lead wire and wire nuts included



Model	Finishes
-------	----------

5022-30BK	Black on Aluminum
5022-30BZ	Bronze on Aluminum
5022-30BBR	Bronze on Brass


3" INGROUND 120V

Integral brightness control, adjustable beam angle



Power 3W to 11.5W
 Brightness 65lm to 515lm
 Beam Angle 15° to 60°
 CRI 85
 Color Temp 3000K Pure White
 Rated Life 45,000 hours
 Listing IP-67

6' lead wire and wire nuts included



Model	Finishes
-------	----------

5032-30BZ	Bronze on Aluminum
5032-30BBR	Bronze on Brass

BOLLARDS 120V-277V



Scoop
See pages 65-66



Chamber
See pages 67-68



Tower
See pages 69-70



Park
See pages 71-72




SHINING FROM THE BACKGROUND

Like professional stagehands, these high-performers easily disappear into the backdrop with their diminutive sizes while adaptably making the whole show possible

Featuring product: **5012-30BZ** Accent

SUBMERSIBLE OUTDOOR TAPE LIGHTING



SUBMERSIBLE OUTDOOR TAPE LIGHTING




1838 listed

- IP-68 rated, UL/cUL listed for wet location
- May be field cut every 6 inches at the end of a run
- Maximum run length of 28ft per electrical feed

Power	3.5W /ft
Brightness	Up to 220 lm /ft
CRI	90
Rated Life	80,000 hours

Double insulated PVC encasement and distinct electrical and mechanical junctions allow for seemingly endless runs that can be powered separately





TAPE SELECTIONS

System	Color Temp	Length	Color
LED-TO2427	2700K	1 1 foot	WT White
LED-TO2430	3000K	5 5 feet	
LED-TO2435	3500K	10 10 feet	

EXAMPLE: LED-TO2435-10-WT


CLASS 2 POWER SUPPLY FOR PRO OUTDOOR (REQUIRED)

Type	Model	Power	Input	Output	Dimmable
Remote Damp Location	 EN-OD24100-RB2-T	96W	120V AC	24V AC	ELV Includes a 6 foot lead wire
Remote Wet Location	 EN-O24100-RB2-T	96W	120V - 277V AC	24V DC	0-10V Includes a 6 foot lead wire

	 Surface mounting clip Secures on both edges	LED-TO24-C1	10 pcs 20 Screws
	 Edge mounting clip Secures on one edge	LED-TO24-C2	10 pcs 10 Screws
	 Invisible clip Holds from the underside	LED-TO24-C3	10 pcs 10 Screws
Clear Channel LED-TO24-CH5	5 feet		


Includes a diffuser, two end caps, and five screws
Snap in to hold Pro Outdoor, Palette Outdoor or Landscape.

Clips to hold indoor InvisiLED tapes For Pro Outdoor, Palette Outdoor, or Landscape Tape Light


	3-Way "Y" Connector Connects tape sections	LED-TO24-Y		Joiner Cable Extends distance between transformers and controllers	LED-TO24-IC6 6 in LED-TO24-IC12 12 in LED-TO24-IC72 72 in LED-TO24-IC120 120 in
	4-Way "X" Connector Connects tape sections	LED-TO24-X	Compatible with Pro Outdoor, Palette Outdoor, Landscape Tape Light		
				End cap 1 cut and 1 male end cap	LED-TO24-EC Black

Compatible with Pro Outdoor, Landscape Tape Light

SUBMERSIBLE OUTDOOR TAPE LIGHTING



- IP-68 rated, UL/cUL listed for wet location
- Variable colors with 3500K White
- DMX and wireless controller options for Palette outdoor system
- Maximum run length of 40 feet
- May be field cut every 2 inches at the end of a run
- Dim with wired controller and wireless controller accessory




Power 1.5W /ft
 Brightness 40 lm /ft on 3500K Setting
 Rated Life 80,000 hours

TAPE SELECTION




System	Length	Type
LED-TCO	1 1' Foot	RGB Color Changing
	5 5' Feet	
	10 10' Feet	



Example: **LED-TCO-5-RGB**

CLASS 2 POWER SUPPLY FOR PALETTE OUTDOOR (REQUIRED)


Type	Model	Power	Input	Output
Remote Wet Location 	EN-O24100-RB2-T	96W	120V - 277V AC	24V DC Includes a 6 foot lead wire

ACCESSORIES FOR PALETTE OUTDOOR

 Signal Wire Master to Slave controller or Slave to Slave	LED-TO24-SW60 LED-TO24-SW120	60 in 120 in
 DMX Signal Wire DMX to Master controller	LED-TO24-MW60 LED-TO24-MW120	60 in 120 in
 RGB Joiner Cable Extends distance between tape and to controllers	LED-TO24-IC6-RGB LED-TO24-IC12-RGB LED-TO24-IC72-RGB LED-TO24-IC120-RGB	6 in 12 in 72 in 120 in

 3-Way "Y" Connector Connects tape sections	LED-TO24-Y-RGB
 4 Way "X" Connector Connects tape sections	LED-TO24-X-RGB




Compatible with Palette Outdoor



Double insulated PVC encasement and distinct electrical and mechanical junctions allow for seemingly endless runs that can be powered separately

CONTROLLER FOR PALETTE OUTDOOR (REQUIRED)

Master Controller (required) 	LED-TO24-CM	4 function wired controller
Wireless Controller (required) 	LED-TO24-WS	4 function wireless controller
Slave Controller (optional) 	LED-TO24-CS	Connects to Master Controller, adding 40 ft run Compatible with Palette Outdoor

 Surface Mounting Clip Secures on both edges	LED-TO24-C1	10 pcs 20 Screws
 Edge Mounting Clip Secures on one edge	LED-TO24-C2	10 pcs 10 Screws
 Invisible Clip Holds from the underside	LED-TO24-C3	10 pcs 10 Screws

Clips to hold indoor InvisiLED tapes, Pro Outdoor, Palette Outdoor, Landscape Tape Light

 End Cap 1 cut and 1 male end cap	LED-TO24-EC	Black
---	--------------------	-------

Compatible with Pro Outdoor, Palette Outdoor, Landscape Tape Light


 Clear Channel	LED-TO24-CH5	5 feet
---	---------------------	--------

Includes a diffuser, two end caps, and five screws.(Pro Outdoor, Palette Outdoor, Landscape Tape Light snap in to hold outdoor InvisiLED tapes).

SUBMERSIBLE OUTDOOR TAPE LIGHTING




Featured Product: **LED-TCO-5-RGB** with **LED-TO24-CH5**



Endurance™ LED BRICK LIGHTS




- Factory-sealed LED light engine
- Die-cast aluminum construction
- 120V direct wire - no driver needed
- Easily retrofit most existing incandescent brick light installations with this maintenance-free LED upgrade



WL-5105
Opal

Input	120V	3000K	<i>Pure White</i>
Power	5.5W	WL-5105-30	aBK <i>Architectural Black</i>
Brightness	Up to 110 lm		aBZ <i>Architectural Bronze</i>
CRI	90		aGH <i>Architectural Graphite</i>
Dimming:	100% - 10% ELV		aWT <i>Architectural White</i>
Rated Life	80,000 hours		




WL-5205
Louver

Input	120V	3000K	<i>Pure White</i>
Power	5.5W	WL-5205-30	aBK <i>Architectural Black</i>
Brightness	Up to 45 lm		aBZ <i>Architectural Bronze</i>
CRI	90		aGH <i>Architectural Graphite</i>
Dimming:	100% - 10% ELV		aWT <i>Architectural White</i>
Rated Life	80,000 hours		



Endurance™ LED FLOOD LIGHTS

NOW AVAILABLE IN A HIGHER POWER OPTION AND ARCHITECTURAL BLACK



Input	120V
CRI	90
Dimming:	100% - 10% ELV
Rated Life	54,000 hours

- Breathable waterproof technology and factory-sealed LED light engine ensures fixture can maintain stable atmospheric pressure and prevent condensation
- Die-cast aluminum construction
- 120V direct wire—no driver needed
- 1/2" threaded heavy-duty mounting arm
- Photo or motion sensor sold separately

			Power	Comparable	Color Temp	Delivered Lumens	Finish
	Flood	WP-LED335	35.5W	100W HID	30 3000K 50 5000K	2450 2730	aBK Architectural Black aBZ Architectural Bronze aGH Architectural Graphite aWT Architectural White
	Flood Pro	WP-LED354	53W	150W HID	35 3500K	3445	

Example: **WP-LED354-35-aWT**


MOTION SENSOR (120V)

Available in 4 complementary colors



PHOTOSENSOR (120V)

Available in 4 complementary colors



Endurance™ LED FLOOD LIGHTS

SINGLE SPOT




Input: 120V
CRI: 85
Dimming: 100% - 10% ELV
Rated Life: 39,000 hours

- Factory-sealed LED light engine
- Die-cast aluminum construction
- 120V direct wire - no driver needed
- Photo/motion sensor sold separately

		Power	Comparable	Color Temp	Delivered		Finish
					Lumens		
	WP-LED415	15W	75W Halogen	30	3000K	965	aBK Architectural Black aBZ Architectural Bronze aGH Architectural Graphite aWT Architectural White
				50	5000K	1030	

Example: WP-LED415-30-AWT

PHOTOSENSOR (120V)
 Available in 4 complementary colors



MOTION SENSOR (120V)
 Available in 4 complementary colors



Endurance™ LED FLOOD LIGHTS

DOUBLE SPOT



Input: 120V
CRI: 85
Dimming: 100% - 10% ELV
Rated Life: 39,000 hours


- Factory-sealed LED light engine
- Die-cast aluminum construction
- 120V direct wire - no driver needed
- Photo/motion sensor sold separately

		Power	Comparable	Color Temp	Delivered Lumens	Finish
		WP-LED430 30W	2 x 75W Halogen	30 3000K	965 x2	aBK Architectural Black aBZ Architectural Bronze aGH Architectural Graphite aWT Architectural White
				50 5000K	1030 x2	

Example: WP-LED430-30-ABZ

PHOTOSENSOR (120V)

Available in 4 complementary colors



MOTION SENSOR (120V)

Available in 4 complementary colors



Endurance™ LED ADJUSTABLE FLOOD LIGHT

- Factory-sealed LED light engine
- Die-cast aluminum construction
- 120V direct wire - no driver needed




Safety cable recommended for extensions over 36"

Rotate to continuously adjust beam angles indexed at 15°, 25°, 40°, 60°

Detachable Shroud

DOUBLE WP-LED529




Input	120V
Power	30W
Brighthness	Up to 1140 lm x2
Comparable	150W x2 PAR 38
Color Temp	3000K & 4000K
CRI	85
Dimming:	100% - 10% ELV
Rated Life	50,000 hours

3000K & 4000K Pure White

WP-LED529-30	aBK Architectural Black
WP-LED529-40	aBZ Architectural Bronze
	aGH Architectural Graphite
	aWT Architectural White






Comes with extension rod kit to extend up to 48" total



**SINGLE
WP-LED514**



Input	120V
Power	15W
Brightness	Up to 1140 lm
Comparable	150W PAR 38
Color Temp	3000K & 4000K
CRI	85
Dimming:	100% - 10% ELV
Rated Life	50,000 hours

3000K & 4000K *Pure White*

aBK	<i>Architectural Black</i>
aBZ	<i>Architectural Bronze</i>
aGH	<i>Architectural Graphite</i>
aWT	<i>Architectural White</i>

Endurance™ LED WALL PACKS




FIN

- Factory-sealed LED light engine
- Die-cast aluminum construction
- 20° forward throw illumination
- Built-in level for easy adjustment
- Photo/Motion sensor sold separately



Tempered Prismatic Glass
Reduces glare while optimizing light distribution



Input	120V-277V
Power	19W/27W
Brigthness	Delivered 1390/2075/2750 lm
Comparable	39W/70W/100W HID
Color Temp	3000K
CRI	85
Dimming:	100% - 10% ELV or 0-10V
Rated Life	100,000 hours

MOTION SENSOR (120V)
Available in 3 complementary colors



- MS-120-BZ** *Bronze*
- MS-120-GY** *Gray*
- MS-120-WT** *White*

3000K *Pure White*

- WP-LED119-30** **aBZ** *Architectural Bronze*
- WP-LED127-30** **aGH** *Architectural Graphite*
- WP-LED135-30** **aWT** *Architectural White*


PHOTOSENSOR (120V)
Available in 3 complementary colors



- PC-120-BZ** *Bronze*
- PC-120-GY** *Gray*
- PC-120-WT** *White*

HAWK

- Factory-sealed LED light engine
- Die-cast aluminum construction
- 20° forward throw illumination
- Built-in level for easy adjustment
- Photo/Motion sensor sold separately



Input	120V-277V
Power	19W/27W
Brighthness	Delivered 1345 lm/2050 lm
Comparable	39W HID/70W HID
Color Temp	3000K
CRI	85
Dimming:	100% - 10% ELV or 0-10V
Rated Life	100,000 hours



3000K

Pure White

WP-LED219-30	aBZ	<i>Architectural Bronze</i>
WP-LED227-30	aGH	<i>Architectural Graphite</i>
	aWT	<i>Architectural White</i>



Mounts in any orientation
For direct and indirect illumination



Includes box sleeve. For use with
surface mount junction boxes

MOTION SENSOR (120V)

Available in 3 complementary colors



MS-120-BZ	<i>Bronze</i>
MS-120-GY	<i>Gray</i>
MS-120-WT	<i>White</i>

PHOTOSENSOR (120V)


Available in 3 complementary colors



PC-120-BZ	<i>Bronze</i>
PC-120-GY	<i>Gray</i>
PC-120-WT	<i>White</i>

RUBIX LED DECORATIVE CEILING MOUNTS

Input: 120-277V Color Temp: 3000K Pure White
 Dimming: 100% - 10% CRI: 90
 ELV or 0-10V Rated Life: 70,000 hours




- Ceiling mount
- Die-cast aluminum construction

Beam 86°
 Power 16W
 Brightness 750 lm

FM-W2505

- AL** Brushed Aluminum
- BK** Black
- BZ** Bronze
- GH** Graphite
- WT** White

Example: FM-W2505-BK



- Ceiling mount
- Die-cast aluminum construction

Beam 95°
 Power 30W
 Brightness 1875 lm

FM-W2510

- AL** Brushed Aluminum
- BK** Black
- BZ** Bronze
- GH** Graphite
- WT** White

Example: FM-W2510-BK

RUBIX & SCOOP LED DECORATIVE WALL MOUNTS

- Mounts up or down
- Die-cast aluminum construction

Input: 120-277V Color Temp: 3000K Pure White
 Dimming: 100% - 10% ELV or 0-10V CRI: 90
 Rated Life: 70,000 hours




WALL MOUNT



SCOOP WALL MOUNT



Single light WS-W2504




Beam 86°
 Power 16W
 Brightness 750 lm

Up & Down light WS-W2505

Beam 86°
 Power 30W
 Brightness 1400 lm

WS-W2504 **AL** *Brushed Aluminum*
WS-W2505 **BK** *Black*
BZ *Bronze*
GH *Graphite*
WT *White*



Beam 86°
 Power 16W
 Brightness 805 lm

WS-W20506 **AL** *Brushed Aluminum*
BK *Black*
BZ *Bronze*
GH *Graphite*
WT *White*

Example: WS-W2504-BZ

Example: WS-W20506-BK



WALL MOUNT



Single light WS-W2509



Beam 86°
 Power 16W
 Brightness 805 lm

- Mounts up or down
- Die-cast aluminum construction

WS-W2509 **AL** *Brushed Aluminum*
BK *Black*
BZ *Bronze*
GH *Graphite*
WT *White*

WALL MOUNT



Up & Down light WS-W2510



Beam 86°
 Power 30W
 Brightness 1385 lm


WS-W2510 **AL** *Brushed Aluminum*
BK *Black*
BZ *Bronze*
GH *Graphite*
WT *White*

Example: WS-W2509-WT

Example: WS-W2510-WT

TUBE LED DECORATIVE CEILING MOUNT

PENDANT




- Die-cast aluminum construction
- Hang straight swivel
- Three 12" and one 6" down rods included
- Dark Sky Friendly

Beam 33°
 Power 16W
 Brightness 800 lm


PD-W2605

- WT** White
- BK** Black
- BZ** Bronze
- GH** Graphite
- AL** Brushed Aluminum

Example: PD-W2605-BK



TUBE LED DECORATIVE CEILING MOUNT




- Ceiling mount
- Die-cast aluminum construction
- Dark Sky Friendly

Beam 35°
 Power 16W
 Brightness 800 lm

FM-W2605

- WT** White
- BK** Black
- BZ** Bronze
- GH** Graphite
- AL** Brushed Aluminum

Example: FM-W2605-WT



- Ceiling mount
- Die-cast aluminum construction

Beam 91°
 Power 30W
 Brightness 1740 lm

FM-W2612

- WT** White
- BK** Black
- BZ** Bronze
- GH** Graphite
- AL** Brushed Aluminum


Example: FM-W2612-GH

TUBE LED DECORATIVE WALL MOUNTS

Input: 120-277V Color Temp: 3000K Pure White
 Dimming: 100% - 10% ELV or 0-10V CRI: 90
 Rated Life: 70,000 hours



4" SINGLE LIGHT WALL MOUNT



- Mounts up or down
- Die-cast aluminum construction

Beam 33°
 Power 16W
 Brightness 800 lm


WS-W2605

WT White
BK Black
BZ Bronze
GH Graphite
AL Brushed Aluminum

Example: WS-W2605-AL



4" DOUBLE LIGHT WALL MOUNT



- Die-cast aluminum construction

Beam 33°
 Power 30W
 Brightness 1750 lm

WS-W2604

WT White
BK Black
BZ Bronze
GH Graphite
AL Brushed Aluminum

Example: WS-W2604-AL



SINGLE LIGHT WALL MOUNT



- Mounts up or down
- Die-cast aluminum construction

Beam 70°
 Power 16W
 Brightness 825 lm

WS-W2609

WT White
BK Black
BZ Bronze
GH Graphite
AL Brushed Aluminum

Example: WS-W2609-BK



DOUBLE LIGHT WALL MOUNT



- Die-cast aluminum construction

Beam 70°
 Power 30W
 Brightness 1525 lm

WS-W2610


WT White
BK Black
BZ Bronze
GH Graphite
AL Brushed Aluminum

Example: WS-W2610-BK

LANDSCAPE LED LANDSCAPE


GRAND ACCENT 12V PHOTOMETRICS

At 15° Setting




POWER	15W		22W		26W		30W		33W	
DISTANCE	FOOT CANDLES	BEAM WIDTH	FOOT CANDLES	BEAM WIDTH	FOOT CANDLES	BEAM WIDTH	FOOT CANDLES	BEAM WIDTH	FOOT CANDLES	BEAM WIDTH
4ft	260.4fc	1.1ft	418.4fc	1.1ft	465.4fc	1.1ft	521.4fc	1.1ft	549.3fc	1.1ft
8ft	65.1fc	2.1ft	104.6fc	2.1ft	116.4fc	2.1ft	130.4fc	2.1ft	137.3fc	2.1ft
12ft	28.9fc	3.2ft	46.5fc	3.2ft	51.7fc	3.2ft	57.9fc	3.2ft	61.0fc	3.2ft
16ft	16.3fc	4.2ft	26.2fc	4.2ft	29.1fc	4.2ft	32.6fc	4.2ft	34.3fc	4.2ft
24ft	7.2fc	6.3ft	11.6fc	6.3ft	12.9fc	6.3ft	14.5fc	6.3ft	15.3fc	6.3ft
32ft	4.1fc	8.4ft	6.5fc	8.4ft	7.3fc	8.4ft	8.1fc	8.4ft	8.6fc	8.4ft
40ft	2.6fc	10.5ft	4.2fc	10.5ft	4.7fc	10.5ft	5.2fc	10.5ft	5.5fc	10.5ft
48ft	1.8fc	12.6ft	2.9fc	12.6ft	3.2fc	12.6ft	3.6fc	12.6ft	3.8fc	12.6ft
60ft	1.2fc	15.8ft	1.9fc	15.8ft	2.1fc	15.8ft	2.3fc	15.8ft	2.4fc	15.8ft

At 25° Setting




POWER	15W		22W		26W		30W		33W	
DISTANCE	FOOT CANDLES	BEAM WIDTH	FOOT CANDLES	BEAM WIDTH	FOOT CANDLES	BEAM WIDTH	FOOT CANDLES	BEAM WIDTH	FOOT CANDLES	BEAM WIDTH
4ft	198.0fc	1.8ft	323.3fc	1.8ft	362.6fc	1.8ft	399.3fc	1.8ft	418.4fc	1.8ft
8ft	49.5fc	3.5ft	80.8fc	3.5ft	90.7fc	3.5ft	99.8fc	3.5ft	104.6fc	3.5ft
12ft	22.0fc	5.3ft	35.9fc	5.3ft	40.3fc	5.3ft	44.4fc	5.3ft	46.5fc	5.3ft
16ft	12.4fc	7.1ft	20.2fc	7.1ft	22.7fc	7.1ft	25.0fc	7.1ft	26.2fc	7.1ft
24ft	5.5fc	10.6ft	9.0fc	10.6ft	10.1fc	10.6ft	11.1fc	10.6ft	11.6fc	10.6ft
32ft	3.1fc	14.2ft	5.1fc	14.2ft	5.7fc	14.2ft	6.2fc	14.2ft	6.5fc	14.2ft
40ft	2.0fc	17.7ft	3.2fc	17.7ft	3.6fc	17.7ft	4.0fc	17.7ft	4.2fc	17.7ft
48ft	1.4fc	21.3ft	2.2fc	21.3ft	2.5fc	21.3ft	2.8fc	21.3ft	2.9fc	21.3ft
60ft	0.9fc	26.6ft	1.4fc	26.6ft	1.6fc	26.6ft	1.8fc	26.6ft	1.9fc	26.6ft

At 40° Setting



POWER	15W		22W		26W		30W		33W	
DISTANCE	FOOT CANDLES	BEAM WIDTH	FOOT CANDLES	BEAM WIDTH	FOOT CANDLES	BEAM WIDTH	FOOT CANDLES	BEAM WIDTH	FOOT CANDLES	BEAM WIDTH
4ft	107.4fc	2.9ft	167.4fc	2.9ft	191.5fc	2.9ft	210.8fc	2.9ft	223.2fc	2.9ft
8ft	26.8fc	5.8ft	41.9fc	5.8ft	47.9fc	5.8ft	52.7fc	5.8ft	55.8fc	5.8ft
12ft	11.9fc	8.7ft	18.6fc	8.7ft	21.3fc	8.7ft	23.4fc	8.7ft	24.8fc	8.7ft
16ft	6.7fc	11.6ft	10.5fc	11.6ft	12.0fc	11.6ft	13.2fc	11.6ft	13.9fc	11.6ft
24ft	3.0fc	17.5ft	4.7fc	17.5ft	5.3fc	17.5ft	5.9fc	17.5ft	6.2fc	17.5ft
32ft	1.7fc	23.3ft	2.6fc	23.3ft	3.0fc	23.3ft	3.3fc	23.3ft	3.5fc	23.3ft
40ft	1.1fc	29.1ft	1.7fc	29.1ft	1.9fc	29.1ft	2.1fc	29.1ft	2.2fc	29.1ft
48ft	0.7fc	34.9ft	1.2fc	34.9ft	1.3fc	34.9ft	1.5fc	34.9ft	1.5fc	34.9ft
60ft	0.5fc	43.7ft	0.7fc	43.7ft	0.9fc	43.7ft	0.9fc	43.7ft	1.0fc	43.7ft

At 60° Setting




POWER	15W		22W		26W		30W		33W	
DISTANCE	FOOT CANDLES	BEAM WIDTH	FOOT CANDLES	BEAM WIDTH	FOOT CANDLES	BEAM WIDTH	FOOT CANDLES	BEAM WIDTH	FOOT CANDLES	BEAM WIDTH
4ft	50.1fc	4.6ft	79.4fc	4.6ft	91.6fc	4.6ft	100.1fc	4.6ft	105.4fc	4.6ft
8ft	12.5fc	9.2ft	19.8fc	9.2ft	22.9fc	9.2ft	25.0fc	9.2ft	26.3fc	9.2ft
12ft	5.6fc	13.9ft	8.8fc	13.9ft	10.2fc	13.9ft	11.1fc	13.9ft	11.7fc	13.9ft
16ft	3.1fc	18.5ft	5.0fc	18.5ft	5.7fc	18.5ft	6.3fc	18.5ft	6.6fc	18.5ft
24ft	1.4fc	27.7ft	2.2fc	27.7ft	2.5fc	27.7ft	2.8fc	27.7ft	2.9fc	27.7ft
32ft	0.8fc	37.0ft	1.2fc	37.0ft	1.4fc	37.0ft	1.6fc	37.0ft	1.6fc	37.0ft
40ft	0.5fc	46.2ft	0.8fc	46.2ft	0.9fc	46.2ft	1.0fc	46.2ft	1.1fc	46.2ft
48ft	0.3fc	55.4ft	0.6fc	55.4ft	0.6fc	55.4ft	0.7fc	55.4ft	0.7fc	55.4ft
60ft	0.2fc	69.3ft	0.4fc	69.3ft	0.4fc	69.3ft	0.4fc	69.3ft	0.5fc	69.3ft

LANDSCAPE LED LANDSCAPE


GRAND ACCENT 120V PHOTOMETRICS

At 15° Setting




POWER	13W		16W		21W		26W		31W	
DISTANCE	FOOT CANDLES	BEAM WIDTH	FOOT CANDLES	BEAM WIDTH	FOOT CANDLES	BEAM WIDTH	FOOT CANDLES	BEAM WIDTH	FOOT CANDLES	BEAM WIDTH
4ft	298.8fc	1.1ft	356.4fc	1.1ft	457.7fc	1.1ft	541.1fc	1.1ft	613.5fc	1.1ft
8ft	74.7fc	2.1ft	89.1fc	2.1ft	114.4fc	2.1ft	135.3fc	2.1ft	153.4fc	2.1ft
12ft	33.2fc	3.2ft	39.6fc	3.2ft	50.9fc	3.2ft	60.1fc	3.2ft	68.2fc	3.2ft
16ft	18.7fc	4.2ft	22.3fc	4.2ft	28.6fc	4.2ft	33.8fc	4.2ft	38.3fc	4.2ft
24ft	8.3fc	6.3ft	9.9fc	6.3ft	12.7fc	6.3ft	15.0fc	6.3ft	17.0fc	6.3ft
32ft	4.7fc	8.4ft	5.6fc	8.4ft	7.2fc	8.4ft	8.5fc	8.4ft	9.6fc	8.4ft
40ft	3.0fc	10.5ft	3.6fc	10.5ft	4.6fc	10.5ft	5.4fc	10.5ft	6.1fc	10.5ft
48ft	2.1fc	12.6ft	2.5fc	12.6ft	3.2fc	12.6ft	3.8fc	12.6ft	4.3fc	12.6ft
60ft	1.3fc	15.8ft	1.6fc	15.8ft	2.0fc	15.8ft	2.4fc	15.8ft	2.7fc	15.8ft

At 25° Setting




POWER	13W		16W		21W		26W		31W	
DISTANCE	FOOT CANDLES	BEAM WIDTH	FOOT CANDLES	BEAM WIDTH	FOOT CANDLES	BEAM WIDTH	FOOT CANDLES	BEAM WIDTH	FOOT CANDLES	BEAM WIDTH
4ft	238.8fc	1.8ft	281.6fc	1.8ft	356.1fc	1.8ft	424.5fc	1.8ft	474.8fc	1.8ft
8ft	59.7fc	3.5ft	70.4fc	3.5ft	89.0fc	3.5ft	106.1fc	3.5ft	118.7fc	3.5ft
12ft	26.5fc	5.3ft	31.3fc	5.3ft	39.6fc	5.3ft	47.2fc	5.3ft	52.8fc	5.3ft
16ft	14.9fc	7.1ft	17.6fc	7.1ft	22.3fc	7.1ft	26.5fc	7.1ft	29.7fc	7.1ft
24ft	6.6fc	10.6ft	7.8fc	10.6ft	9.9fc	10.6ft	11.8fc	10.6ft	13.2fc	10.6ft
32ft	3.7fc	14.2ft	4.4fc	14.2ft	5.6fc	14.2ft	6.6fc	14.2ft	7.4fc	14.2ft
40ft	2.4fc	17.7ft	2.8fc	17.7ft	3.6fc	17.7ft	4.2fc	17.7ft	4.7fc	17.7ft
48ft	1.7fc	21.3ft	2.0fc	21.3ft	2.5fc	21.3ft	2.9fc	21.3ft	3.3fc	21.3ft
60ft	1.1fc	26.6ft	1.3fc	26.6ft	1.6fc	26.6ft	1.9fc	26.6ft	2.1fc	26.6ft

At 40° Setting



POWER	13W		16W		21W		26W		31W	
DISTANCE	FOOT CANDLES	BEAM WIDTH	FOOT CANDLES	BEAM WIDTH	FOOT CANDLES	BEAM WIDTH	FOOT CANDLES	BEAM WIDTH	FOOT CANDLES	BEAM WIDTH
4ft	113.6fc	2.9ft	136.1fc	2.9ft	175.2fc	2.9ft	204.2fc	2.9ft	234.2fc	2.9ft
8ft	28.4fc	5.8ft	34.0fc	5.8ft	43.8fc	5.8ft	51.0fc	5.8ft	58.5fc	5.8ft
12ft	12.6fc	8.7ft	15.1fc	8.7ft	19.5fc	8.7ft	22.7fc	8.7ft	26.0fc	8.7ft
16ft	7.1fc	11.6ft	8.5fc	11.6ft	10.9fc	11.6ft	12.8fc	11.6ft	14.6fc	11.6ft
24ft	3.2fc	17.5ft	3.8fc	17.5ft	4.9fc	17.5ft	5.7fc	17.5ft	6.5fc	17.5ft
32ft	1.8fc	23.3ft	2.1fc	23.3ft	2.7fc	23.3ft	3.2fc	23.3ft	3.7fc	23.3ft
40ft	1.1fc	29.1ft	1.4fc	29.1ft	1.8fc	29.1ft	2.0fc	29.1ft	2.3fc	29.1ft
48ft	0.8fc	34.9ft	0.9fc	34.9ft	1.2fc	34.9ft	1.4fc	34.9ft	1.6fc	34.9ft
60ft	0.5fc	43.7ft	0.6fc	43.7ft	0.8fc	43.7ft	0.9fc	43.7ft	1.0fc	43.7ft

At 60° Setting




POWER	13W		16W		21W		26W		31W	
DISTANCE	FOOT CANDLES	BEAM WIDTH	FOOT CANDLES	BEAM WIDTH	FOOT CANDLES	BEAM WIDTH	FOOT CANDLES	BEAM WIDTH	FOOT CANDLES	BEAM WIDTH
4ft	53.5fc	4.6ft	64.2fc	4.6ft	81.9fc	4.6ft	97.1fc	4.6ft	110.1fc	4.6ft
8ft	13.4fc	9.2ft	16.0fc	9.2ft	20.5fc	9.2ft	24.3fc	9.2ft	27.5fc	9.2ft
12ft	5.9fc	13.9ft	7.1fc	13.9ft	9.1fc	13.9ft	10.8fc	13.9ft	12.2fc	13.9ft
16ft	3.3fc	18.5ft	4.0fc	18.5ft	5.1fc	18.5ft	6.1fc	18.5ft	6.9fc	18.5ft
24ft	1.5fc	27.7ft	1.8fc	27.7ft	2.3fc	27.7ft	2.7fc	27.7ft	3.1fc	27.7ft
32ft	0.8fc	37.0ft	1.0fc	37.0ft	1.3fc	37.0ft	1.5fc	37.0ft	1.7fc	37.0ft
40ft	0.5fc	46.2ft	0.6fc	46.2ft	0.8fc	46.2ft	1.0fc	46.2ft	1.1fc	46.2ft
48ft	0.4fc	55.4ft	0.4fc	55.4ft	0.6fc	55.4ft	0.7fc	55.4ft	0.8fc	55.4ft
60ft	0.2fc	69.3ft	0.3fc	69.3ft	0.4fc	69.3ft	0.4fc	69.3ft	0.5fc	69.3ft

LANDSCAPE LED LANDSCAPE


ACCENT 12V PHOTOMETRICS

At 10° Setting




POWER	2W		4W		8W		12W		16W	
DISTANCE	FOOT CANDLES	BEAM WIDTH	FOOT CANDLES	BEAM WIDTH	FOOT CANDLES	BEAM WIDTH	FOOT CANDLES	BEAM WIDTH	FOOT CANDLES	BEAM WIDTH
4ft	55.9fc	0.8ft	129.0fc	0.8ft	233.8fc	0.8ft	341.4fc	0.8ft	435.3fc	0.8ft
8ft	14.0fc	1.7ft	32.3fc	1.7ft	58.5fc	1.7ft	85.4fc	1.7ft	108.8fc	1.7ft
12ft	6.2fc	2.5ft	14.3fc	2.5ft	26.0fc	2.5ft	37.9fc	2.5ft	48.4fc	2.5ft
16ft	3.5fc	3.4ft	8.1fc	3.4ft	14.6fc	3.4ft	21.3fc	3.4ft	27.2fc	3.4ft
24ft	1.6fc	5.0ft	3.6fc	5.0ft	6.5fc	5.0ft	9.5fc	5.0ft	12.1fc	5.0ft
32ft	0.9fc	6.7ft	2.0fc	6.7ft	3.7fc	6.7ft	5.3fc	6.7ft	6.8fc	6.7ft
40ft	0.6fc	8.4ft	1.3fc	8.4ft	2.3fc	8.4ft	3.4fc	8.4ft	4.4fc	8.4ft
48ft	0.4fc	10.1ft	0.9fc	10.1ft	1.6fc	10.1ft	2.4fc	10.1ft	3.0fc	10.1ft
60ft	0.2fc	12.6ft	0.6fc	12.6ft	1.0fc	12.6ft	1.5fc	12.6ft	1.9fc	12.6ft

At 25° Setting




POWER	2W		4W		8W		12W		16W	
DISTANCE	FOOT CANDLES	BEAM WIDTH	FOOT CANDLES	BEAM WIDTH	FOOT CANDLES	BEAM WIDTH	FOOT CANDLES	BEAM WIDTH	FOOT CANDLES	BEAM WIDTH
4ft	25.2fc	1.8ft	54.8fc	1.8ft	105.8fc	1.8ft	153.0fc	1.8ft	194.6fc	1.8ft
8ft	6.3fc	3.5ft	13.7fc	3.5ft	26.5fc	3.5ft	38.3fc	3.5ft	48.7fc	3.5ft
12ft	2.8fc	5.3ft	6.1fc	5.3ft	11.8fc	5.3ft	17.0fc	5.3ft	21.6fc	5.3ft
16ft	1.6fc	7.1ft	3.4fc	7.1ft	6.6fc	7.1ft	9.6fc	7.1ft	12.2fc	7.1ft
24ft	0.7fc	10.6ft	1.5fc	10.6ft	2.9fc	10.6ft	4.3fc	10.6ft	5.4fc	10.6ft
32ft	0.4fc	14.2ft	0.9fc	14.2ft	1.7fc	14.2ft	2.4fc	14.2ft	3.0fc	14.2ft
40ft	0.3fc	17.7ft	0.5fc	17.7ft	1.1fc	17.7ft	1.5fc	17.7ft	1.9fc	17.7ft
48ft	0.2fc	21.3ft	0.4fc	21.3ft	0.7fc	21.3ft	1.1fc	21.3ft	1.4fc	21.3ft
60ft	0.1fc	26.6ft	0.2fc	26.6ft	0.5fc	26.6ft	0.7fc	26.6ft	0.9fc	26.6ft

At 40° Setting



POWER	2W		4W		8W		12W		16W	
DISTANCE	FOOT CANDLES	BEAM WIDTH	FOOT CANDLES	BEAM WIDTH	FOOT CANDLES	BEAM WIDTH	FOOT CANDLES	BEAM WIDTH	FOOT CANDLES	BEAM WIDTH
4ft	14.5fc	3.0ft	33.2fc	3.0ft	60.2fc	3.0ft	88.6fc	3.0ft	113.9fc	3.0ft
8ft	3.6fc	6.1ft	8.3fc	6.1ft	15.0fc	6.1ft	22.1fc	6.1ft	28.5fc	6.1ft
12ft	1.6fc	9.1ft	3.7fc	9.1ft	6.7fc	9.1ft	9.8fc	9.1ft	12.7fc	9.1ft
16ft	0.9fc	12.2ft	2.1fc	12.2ft	3.8fc	12.2ft	5.5fc	12.2ft	7.1fc	12.2ft
24ft	0.4fc	18.2ft	0.9fc	18.2ft	1.7fc	18.2ft	2.5fc	18.2ft	3.2fc	18.2ft
32ft	0.2fc	24.3ft	0.5fc	24.3ft	0.9fc	24.3ft	1.4fc	24.3ft	1.8fc	24.3ft
40ft	0.1fc	30.4ft	0.3fc	30.4ft	0.6fc	30.4ft	0.9fc	30.4ft	1.1fc	30.4ft
48ft	0.1fc	36.5ft	0.2fc	36.5ft	0.4fc	36.5ft	0.6fc	36.5ft	0.8fc	36.5ft
60ft	0.1fc	45.6ft	0.1fc	45.6ft	0.3fc	45.6ft	0.4fc	45.6ft	0.5fc	45.6ft

At 60° Setting




POWER	2W		4W		8W		12W		16W	
DISTANCE	FOOT CANDLES	BEAM WIDTH	FOOT CANDLES	BEAM WIDTH	FOOT CANDLES	BEAM WIDTH	FOOT CANDLES	BEAM WIDTH	FOOT CANDLES	BEAM WIDTH
4ft	9.0fc	4.5ft	16.6fc	4.5ft	41.2fc	4.5ft	54.0fc	4.5ft	70.1fc	4.5ft
8ft	2.3fc	8.9ft	4.1fc	8.9ft	10.3fc	8.9ft	13.5fc	8.9ft	17.5fc	8.9ft
12ft	1.0fc	13.4ft	1.8fc	13.4ft	4.6fc	13.4ft	6.0fc	13.4ft	7.8fc	13.4ft
16ft	0.6fc	17.9ft	1.0fc	17.9ft	2.6fc	17.9ft	3.4fc	17.9ft	4.4fc	17.9ft
24ft	0.3fc	26.8ft	0.5fc	26.8ft	1.1fc	26.8ft	1.5fc	26.8ft	1.9fc	26.8ft
32ft	0.1fc	35.8ft	0.3fc	35.8ft	0.6fc	35.8ft	0.8fc	35.8ft	1.1fc	35.8ft
40ft	0.1fc	44.7ft	0.2fc	44.7ft	0.4fc	44.7ft	0.5fc	44.7ft	0.7fc	44.7ft
48ft	0.1fc	53.7ft	0.1fc	53.7ft	0.3fc	53.7ft	0.4fc	53.7ft	0.5fc	53.7ft
60ft	0.0fc	67.1ft	0.1fc	67.1ft	0.2fc	67.1ft	0.2fc	67.1ft	0.3fc	67.1ft

LANDSCAPE LED LANDSCAPE


ACCENT 120V PHOTOMETRICS

At 15° Setting




POWER	3.5W		6.5W		10.5W		13.5W		14.5W	
DISTANCE	FOOT CANDLES	BEAM WIDTH	FOOT CANDLES	BEAM WIDTH	FOOT CANDLES	BEAM WIDTH	FOOT CANDLES	BEAM WIDTH	FOOT CANDLES	BEAM WIDTH
4ft	50.4fc	1.1ft	102.4fc	1.1ft	151.8fc	1.1ft	192.9fc	1.1ft	200.3fc	1.1ft
8ft	12.6fc	2.1ft	25.6fc	2.1ft	37.9fc	2.1ft	48.2fc	2.1ft	50.1fc	2.1ft
12ft	5.6fc	3.2ft	11.4fc	3.2ft	16.9fc	3.2ft	21.4fc	3.2ft	22.3fc	3.2ft
16ft	3.1fc	4.2ft	6.4fc	4.2ft	9.5fc	4.2ft	12.1fc	4.2ft	12.5fc	4.2ft
24ft	1.4fc	6.3ft	2.8fc	6.3ft	4.2fc	6.3ft	5.4fc	6.3ft	5.6fc	6.3ft
32ft	0.8fc	8.4ft	1.6fc	8.4ft	2.4fc	8.4ft	3.0fc	8.4ft	3.1fc	8.4ft
40ft	0.5fc	10.5ft	1.0fc	10.5ft	1.5fc	10.5ft	1.9fc	10.5ft	2.0fc	10.5ft
48ft	0.3fc	12.6ft	0.7fc	12.6ft	1.1fc	12.6ft	1.3fc	12.6ft	1.4fc	12.6ft
60ft	0.2fc	15.8ft	0.5fc	15.8ft	0.7fc	15.8ft	0.9fc	15.8ft	0.9fc	15.8ft

At 25° Setting




POWER	3.5W		6.5W		10.5W		13.5W		14.5W	
DISTANCE	FOOT CANDLES	BEAM WIDTH	FOOT CANDLES	BEAM WIDTH	FOOT CANDLES	BEAM WIDTH	FOOT CANDLES	BEAM WIDTH	FOOT CANDLES	BEAM WIDTH
4ft	37.2fc	1.8ft	73.1fc	1.8ft	113.1fc	1.8ft	139.2fc	1.8ft	149.1fc	1.8ft
8ft	9.3fc	3.5ft	18.3fc	3.5ft	28.3fc	3.5ft	34.8fc	3.5ft	37.3fc	3.5ft
12ft	4.1fc	5.3ft	8.1fc	5.3ft	12.6fc	5.3ft	15.5fc	5.3ft	16.6fc	5.3ft
16ft	2.3fc	7.1ft	4.6fc	7.1ft	7.1fc	7.1ft	8.7fc	7.1ft	9.3fc	7.1ft
24ft	1.0fc	10.6ft	2.0fc	10.6ft	3.1fc	10.6ft	3.9fc	10.6ft	4.1fc	10.6ft
32ft	0.6fc	14.2ft	1.1fc	14.2ft	1.8fc	14.2ft	2.2fc	14.2ft	2.3fc	14.2ft
40ft	0.4fc	17.7ft	0.7fc	17.7ft	1.1fc	17.7ft	1.4fc	17.7ft	1.5fc	17.7ft
48ft	0.3fc	21.3ft	0.5fc	21.3ft	0.8fc	21.3ft	1.0fc	21.3ft	1.0fc	21.3ft
60ft	0.2fc	26.6ft	0.3fc	26.6ft	0.5fc	26.6ft	0.6fc	26.6ft	0.7fc	26.6ft

At 40° Setting



POWER	3.5W		6.5W		10.5W		13.5W		14.5W	
DISTANCE	FOOT CANDLES	BEAM WIDTH	FOOT CANDLES	BEAM WIDTH	FOOT CANDLES	BEAM WIDTH	FOOT CANDLES	BEAM WIDTH	FOOT CANDLES	BEAM WIDTH
4ft	20.7fc	3.0ft	36.7fc	3.0ft	63.4fc	3.0ft	81.9fc	3.0ft	85.9fc	3.0ft
8ft	5.2fc	6.1ft	9.2fc	6.1ft	15.8fc	6.1ft	20.5fc	6.1ft	21.5fc	6.1ft
12ft	2.3fc	9.1ft	4.1fc	9.1ft	7.0fc	9.1ft	9.1fc	9.1ft	9.5fc	9.1ft
16ft	1.3fc	12.2ft	2.3fc	12.2ft	4.0fc	12.2ft	5.1fc	12.2ft	5.4fc	12.2ft
24ft	0.6fc	18.2ft	1.0fc	18.2ft	1.8fc	18.2ft	2.3fc	18.2ft	2.4fc	18.2ft
32ft	0.3fc	24.3ft	0.6fc	24.3ft	1.0fc	24.3ft	1.3fc	24.3ft	1.3fc	24.3ft
40ft	0.2fc	30.4ft	0.4fc	30.4ft	0.6fc	30.4ft	0.8fc	30.4ft	0.9fc	30.4ft
48ft	0.1fc	36.5ft	0.3fc	36.5ft	0.4fc	36.5ft	0.6fc	36.5ft	0.6fc	36.5ft
60ft	0.1fc	45.6ft	0.2fc	45.6ft	0.3fc	45.6ft	0.4fc	45.6ft	0.4fc	45.6ft

At 60° Setting




POWER	3.5W		6.5W		10.5W		13.5W		14.5W	
DISTANCE	FOOT CANDLES	BEAM WIDTH	FOOT CANDLES	BEAM WIDTH	FOOT CANDLES	BEAM WIDTH	FOOT CANDLES	BEAM WIDTH	FOOT CANDLES	BEAM WIDTH
4ft	13.2fc	4.5ft	24.5fc	4.5ft	33.1fc	4.5ft	46.6fc	4.5ft	53.6fc	4.5ft
8ft	3.3fc	8.9ft	6.1fc	8.9ft	8.3fc	8.9ft	11.7fc	8.9ft	13.4fc	8.9ft
12ft	1.5fc	13.4ft	2.7fc	13.4ft	3.7fc	13.4ft	5.2fc	13.4ft	6.0fc	13.4ft
16ft	0.8fc	17.9ft	1.5fc	17.9ft	2.1fc	17.9ft	2.9fc	17.9ft	3.4fc	17.9ft
24ft	0.4fc	26.8ft	0.7fc	26.8ft	0.9fc	26.8ft	1.3fc	26.8ft	1.5fc	26.8ft
32ft	0.2fc	35.8ft	0.4fc	35.8ft	0.5fc	35.8ft	0.7fc	35.8ft	0.8fc	35.8ft
40ft	0.1fc	44.7ft	0.2fc	44.7ft	0.3fc	44.7ft	0.5fc	44.7ft	0.5fc	44.7ft
48ft	0.1fc	53.7ft	0.2fc	53.7ft	0.2fc	53.7ft	0.3fc	53.7ft	0.4fc	53.7ft
60ft	0.1fc	67.1ft	0.1fc	67.1ft	0.1fc	67.1ft	0.2fc	67.1ft	0.2fc	67.1ft

LANDSCAPE LED LANDSCAPE


MINI ACCENT 12V PHOTOMETRICS

At 10° Setting




POWER	1W		2W		4W		6W		7W	
DISTANCE	FOOT CANDLES	BEAM WIDTH	FOOT CANDLES	BEAM WIDTH	FOOT CANDLES	BEAM WIDTH	FOOT CANDLES	BEAM WIDTH	FOOT CANDLES	BEAM WIDTH
4ft	83.1fc	0.6ft	122.8fc	0.6ft	181.0fc	0.6ft	244.1fc	0.6ft	274.9fc	0.6ft
8ft	20.8fc	1.2ft	30.7fc	1.2ft	45.3fc	1.2ft	61.0fc	1.2ft	68.7fc	1.2ft
12ft	9.2fc	1.8ft	13.6fc	1.8ft	20.1fc	1.8ft	27.1fc	1.8ft	30.5fc	1.8ft
16ft	5.2fc	2.3ft	7.7fc	2.3ft	11.3fc	2.3ft	15.3fc	2.3ft	17.2fc	2.3ft
24ft	2.3fc	3.5ft	3.4fc	3.5ft	5.0fc	3.5ft	6.8fc	3.5ft	7.6fc	3.5ft
32ft	1.3fc	4.7ft	1.9fc	4.7ft	2.8fc	4.7ft	3.8fc	4.7ft	4.3fc	4.7ft
40ft	0.8fc	5.9ft	1.2fc	5.9ft	1.8fc	5.9ft	2.4fc	5.9ft	2.7fc	5.9ft
48ft	0.6fc	7.0ft	0.9fc	7.0ft	1.3fc	7.0ft	1.7fc	7.0ft	1.9fc	7.0ft
60ft	0.4fc	8.8ft	0.5fc	8.8ft	0.8fc	8.8ft	1.1fc	8.8ft	1.2fc	8.8ft

At 25° Setting




POWER	1W		2W		4W		6W		7W	
DISTANCE	FOOT CANDLES	BEAM WIDTH	FOOT CANDLES	BEAM WIDTH	FOOT CANDLES	BEAM WIDTH	FOOT CANDLES	BEAM WIDTH	FOOT CANDLES	BEAM WIDTH
4ft	22.8fc	1.9ft	36.0fc	1.9ft	52.7fc	1.9ft	71.1fc	1.9ft	76.8fc	1.9ft
8ft	5.7fc	3.7ft	9.0fc	3.7ft	13.2fc	3.7ft	17.8fc	3.7ft	19.2fc	3.7ft
12ft	2.5fc	5.6ft	4.0fc	5.6ft	5.9fc	5.6ft	7.9fc	5.6ft	8.5fc	5.6ft
16ft	1.4fc	7.4ft	2.2fc	7.4ft	3.3fc	7.4ft	4.4fc	7.4ft	4.8fc	7.4ft
24ft	0.6fc	11.1ft	1.0fc	11.1ft	1.5fc	11.1ft	2.0fc	11.1ft	2.1fc	11.1ft
32ft	0.4fc	14.8ft	0.6fc	14.8ft	0.8fc	14.8ft	1.1fc	14.8ft	1.2fc	14.8ft
40ft	0.2fc	18.5ft	0.4fc	18.5ft	0.5fc	18.5ft	0.7fc	18.5ft	0.8fc	18.5ft
48ft	0.2fc	22.3ft	0.2fc	22.3ft	0.4fc	22.3ft	0.5fc	22.3ft	0.5fc	22.3ft
60ft	0.1fc	27.8ft	0.2fc	27.8ft	0.2fc	27.8ft	0.3fc	27.8ft	0.3fc	27.8ft

At 40° Setting



POWER	1W		2W		4W		6W		7W	
DISTANCE	FOOT CANDLES	BEAM WIDTH	FOOT CANDLES	BEAM WIDTH	FOOT CANDLES	BEAM WIDTH	FOOT CANDLES	BEAM WIDTH	FOOT CANDLES	BEAM WIDTH
4ft	13.0fc	3.1ft	20.7fc	3.1ft	27.7fc	3.1ft	39.6fc	3.1ft	42.0fc	3.1ft
8ft	3.3fc	6.1ft	5.2fc	6.1ft	6.9fc	6.1ft	9.9fc	6.1ft	10.5fc	6.1ft
12ft	1.4fc	9.2ft	2.3fc	9.2ft	3.1fc	9.2ft	4.4fc	9.2ft	4.7fc	9.2ft
16ft	0.8fc	12.3ft	1.3fc	12.3ft	1.7fc	12.3ft	2.5fc	12.3ft	2.6fc	12.3ft
24ft	0.4fc	18.4ft	0.6fc	18.4ft	0.8fc	18.4ft	1.1fc	18.4ft	1.2fc	18.4ft
32ft	0.2fc	24.5ft	0.3fc	24.5ft	0.4fc	24.5ft	0.6fc	24.5ft	0.7fc	24.5ft
40ft	0.1fc	30.6ft	0.2fc	30.6ft	0.3fc	30.6ft	0.4fc	30.6ft	0.4fc	30.6ft
48ft	0.1fc	36.8ft	0.1fc	36.8ft	0.2fc	36.8ft	0.3fc	36.8ft	0.3fc	36.8ft
60ft	0.1fc	45.9ft	0.1fc	45.9ft	0.1fc	45.9ft	0.2fc	45.9ft	0.2fc	45.9ft

At 50° Setting




POWER	1W		2W		4W		6W		7W	
DISTANCE	FOOT CANDLES	BEAM WIDTH	FOOT CANDLES	BEAM WIDTH	FOOT CANDLES	BEAM WIDTH	FOOT CANDLES	BEAM WIDTH	FOOT CANDLES	BEAM WIDTH
4ft	9.0fc	3.9ft	12.3fc	3.9ft	16.9fc	3.9ft	25.0fc	3.9ft	29.8fc	3.9ft
8ft	2.3fc	7.7ft	3.1fc	7.7ft	4.2fc	7.7ft	6.2fc	7.7ft	7.4fc	7.7ft
12ft	1.0fc	11.6ft	1.4fc	11.6ft	1.9fc	11.6ft	2.8fc	11.6ft	3.3fc	11.6ft
16ft	0.6fc	15.5ft	0.8fc	15.5ft	1.1fc	15.5ft	1.6fc	15.5ft	1.9fc	15.5ft
24ft	0.3fc	23.2ft	0.3fc	23.2ft	0.5fc	23.2ft	0.7fc	23.2ft	0.8fc	23.2ft
32ft	0.1fc	30.9ft	0.2fc	30.9ft	0.3fc	30.9ft	0.4fc	30.9ft	0.5fc	30.9ft
40ft	0.1fc	38.7ft	0.1fc	38.7ft	0.2fc	38.7ft	0.2fc	38.7ft	0.3fc	38.7ft
48ft	0.1fc	46.4ft	0.1fc	46.4ft	0.1fc	46.4ft	0.2fc	46.4ft	0.2fc	46.4ft
60ft	0.0fc	58.0ft	0.1fc	58.0ft	0.1fc	58.0ft	0.1fc	58.0ft	0.1fc	58.0ft

LANDSCAPE LED LANDSCAPE


3" INGROUND 12V PHOTOMETRICS

At 15° Setting




POWER	2W		4W		7W		10W		12W	
DISTANCE	FOOT CANDLES	BEAM WIDTH	FOOT CANDLES	BEAM WIDTH	FOOT CANDLES	BEAM WIDTH	FOOT CANDLES	BEAM WIDTH	FOOT CANDLES	BEAM WIDTH
4ft	47.2fc	1.1ft	75.8fc	1.1ft	165.3fc	1.1ft	236.2fc	1.1ft	283.4fc	1.1ft
8ft	11.8fc	2.1ft	18.9fc	2.1ft	41.3fc	2.1ft	59.0fc	2.1ft	70.9fc	2.1ft
12ft	5.2fc	3.2ft	8.4fc	3.2ft	18.4fc	3.2ft	26.2fc	3.2ft	31.5fc	3.2ft
16ft	3.0fc	4.2ft	4.7fc	4.2ft	10.3fc	4.2ft	14.8fc	4.2ft	17.7fc	4.2ft
24ft	1.3fc	6.3ft	2.1fc	6.3ft	4.6fc	6.3ft	6.6fc	6.3ft	7.9fc	6.3ft
32ft	0.7fc	8.4ft	1.2fc	8.4ft	2.6fc	8.4ft	3.7fc	8.4ft	4.4fc	8.4ft
40ft	0.5fc	10.5ft	0.8fc	10.5ft	1.7fc	10.5ft	2.4fc	10.5ft	2.8fc	10.5ft
48ft	0.3fc	12.6ft	0.5fc	12.6ft	1.1fc	12.6ft	1.6fc	12.6ft	2.0fc	12.6ft
60ft	0.2fc	15.8ft	0.3fc	15.8ft	0.7fc	15.8ft	1.0fc	15.8ft	1.3fc	15.8ft

At 30° Setting




POWER	2W		4W		7W		10W		12W	
DISTANCE	FOOT CANDLES	BEAM WIDTH	FOOT CANDLES	BEAM WIDTH	FOOT CANDLES	BEAM WIDTH	FOOT CANDLES	BEAM WIDTH	FOOT CANDLES	BEAM WIDTH
4ft	19.4fc	2.1ft	38.8fc	2.1ft	68.0fc	2.1ft	97.1fc	2.1ft	116.6fc	2.1ft
8ft	4.9fc	4.3ft	9.7fc	4.3ft	17.0fc	4.3ft	24.3fc	4.3ft	29.1fc	4.3ft
12ft	2.2fc	6.4ft	4.3fc	6.4ft	7.6fc	6.4ft	10.8fc	6.4ft	13.0fc	6.4ft
16ft	1.2fc	8.6ft	2.4fc	8.6ft	4.3fc	8.6ft	6.1fc	8.6ft	7.3fc	8.6ft
24ft	0.5fc	12.9ft	1.1fc	12.9ft	1.9fc	12.9ft	2.7fc	12.9ft	3.2fc	12.9ft
32ft	0.3fc	17.1ft	0.6fc	17.1ft	1.1fc	17.1ft	1.5fc	17.1ft	1.8fc	17.1ft
40ft	0.2fc	21.4ft	0.4fc	21.4ft	0.7fc	21.4ft	1.0fc	21.4ft	1.2fc	21.4ft
48ft	0.1fc	25.7ft	0.3fc	25.7ft	0.5fc	25.7ft	0.7fc	25.7ft	0.8fc	25.7ft
60ft	0.1fc	32.2ft	0.2fc	32.2ft	0.3fc	32.2ft	0.4fc	32.2ft	0.5fc	32.2ft

At 45° Setting



POWER	2W		4W		7W		10W		12W	
DISTANCE	FOOT CANDLES	BEAM WIDTH	FOOT CANDLES	BEAM WIDTH	FOOT CANDLES	BEAM WIDTH	FOOT CANDLES	BEAM WIDTH	FOOT CANDLES	BEAM WIDTH
4ft	10.9fc	3.3ft	21.8fc	3.3ft	38.1fc	3.3ft	54.4fc	3.3ft	65.3fc	3.3ft
8ft	2.7fc	6.6ft	5.4fc	6.6ft	9.5fc	6.6ft	13.6fc	6.6ft	16.3fc	6.6ft
12ft	1.2fc	9.9ft	2.4fc	9.9ft	4.2fc	9.9ft	6.0fc	9.9ft	7.3fc	9.9ft
16ft	0.7fc	13.3ft	1.4fc	13.3ft	2.4fc	13.3ft	3.4fc	13.3ft	4.1fc	13.3ft
24ft	0.3fc	19.9ft	0.6fc	19.9ft	1.1fc	19.9ft	1.5fc	19.9ft	1.8fc	19.9ft
32ft	0.2fc	26.5ft	0.3fc	26.5ft	0.6fc	26.5ft	0.9fc	26.5ft	1.0fc	26.5ft
40ft	0.1fc	33.1ft	0.2fc	33.1ft	0.4fc	33.1ft	0.5fc	33.1ft	0.7fc	33.1ft
48ft	0.1fc	39.8ft	0.2fc	39.8ft	0.3fc	39.8ft	0.4fc	39.8ft	0.5fc	39.8ft
60ft	0.0fc	49.7ft	0.1fc	49.7ft	0.2fc	49.7ft	0.2fc	49.7ft	0.3fc	49.7ft

At 60° Setting




POWER	2W		4W		7W		10W		12W	
DISTANCE	FOOT CANDLES	BEAM WIDTH	FOOT CANDLES	BEAM WIDTH	FOOT CANDLES	BEAM WIDTH	FOOT CANDLES	BEAM WIDTH	FOOT CANDLES	BEAM WIDTH
4ft	7.3fc	4.6ft	14.5fc	4.6ft	25.4fc	4.6ft	36.3fc	4.6ft	43.6fc	4.6ft
8ft	1.8fc	9.2ft	3.6fc	9.2ft	6.4fc	9.2ft	9.1fc	9.2ft	10.9fc	9.2ft
12ft	0.8fc	13.9ft	1.6fc	13.9ft	2.8fc	13.9ft	4.0fc	13.9ft	4.8fc	13.9ft
16ft	0.5fc	18.5ft	0.9fc	18.5ft	1.6fc	18.5ft	2.3fc	18.5ft	2.7fc	18.5ft
24ft	0.2fc	27.7ft	0.4fc	27.7ft	0.7fc	27.7ft	1.0fc	27.7ft	1.2fc	27.7ft
32ft	0.1fc	37.0ft	0.2fc	37.0ft	0.4fc	37.0ft	0.6fc	37.0ft	0.7fc	37.0ft
40ft	0.1fc	46.2ft	0.1fc	46.2ft	0.3fc	46.2ft	0.4fc	46.2ft	0.4fc	46.2ft
48ft	0.1fc	55.4ft	0.1fc	55.4ft	0.2fc	55.4ft	0.3fc	55.4ft	0.3fc	55.4ft
60ft	0.0fc	69.3ft	0.1fc	69.3ft	0.1fc	69.3ft	0.2fc	69.3ft	0.2fc	69.3ft

LANDSCAPE LED LANDSCAPE


3" INGROUND 120V PHOTOMETRICS

At 15° Setting




POWER	3W		5.5W		8.5W		10.5W		11.5W	
DISTANCE	FOOT CANDLES	BEAM WIDTH	FOOT CANDLES	BEAM WIDTH	FOOT CANDLES	BEAM WIDTH	FOOT CANDLES	BEAM WIDTH	FOOT CANDLES	BEAM WIDTH
4ft	44.4fc	1.1ft	81.1fc	1.1ft	125.4fc	1.1ft	154.9fc	1.1ft	169.6fc	1.1ft
8ft	11.1fc	2.1ft	20.3fc	2.1ft	31.3fc	2.1ft	38.7fc	2.1ft	42.4fc	2.1ft
12ft	4.9fc	3.2ft	9.0fc	3.2ft	13.9fc	3.2ft	17.2fc	3.2ft	18.8fc	3.2ft
16ft	2.8fc	4.2ft	5.1fc	4.2ft	7.8fc	4.2ft	9.7fc	4.2ft	10.6fc	4.2ft
24ft	1.2fc	6.3ft	2.3fc	6.3ft	3.5fc	6.3ft	4.3fc	6.3ft	4.7fc	6.3ft
32ft	0.7fc	8.4ft	1.3fc	8.4ft	2.0fc	8.4ft	2.4fc	8.4ft	2.7fc	8.4ft
40ft	0.4fc	10.5ft	0.8fc	10.5ft	1.3fc	10.5ft	1.5fc	10.5ft	1.7fc	10.5ft
48ft	0.3fc	12.6ft	0.6fc	12.6ft	0.9fc	12.6ft	1.1fc	12.6ft	1.2fc	12.6ft
60ft	0.2fc	15.8ft	0.4fc	15.8ft	0.6fc	15.8ft	0.7fc	15.8ft	0.8fc	15.8ft

At 30° Setting




POWER	15W		22W		26W		30W		33W	
DISTANCE	FOOT CANDLES	BEAM WIDTH	FOOT CANDLES	BEAM WIDTH	FOOT CANDLES	BEAM WIDTH	FOOT CANDLES	BEAM WIDTH	FOOT CANDLES	BEAM WIDTH
4ft	24.5fc	2.1ft	45.1fc	2.1ft	69.6fc	2.1ft	86.0fc	2.1ft	94.2fc	2.1ft
8ft	6.1fc	4.3ft	11.3fc	4.3ft	17.4fc	4.3ft	21.5fc	4.3ft	23.5fc	4.3ft
12ft	2.7fc	6.4ft	5.0fc	6.4ft	7.7fc	6.4ft	9.6fc	6.4ft	10.5fc	6.4ft
16ft	1.5fc	8.6ft	2.8fc	8.6ft	4.4fc	8.6ft	5.4fc	8.6ft	5.9fc	8.6ft
24ft	0.7fc	12.9ft	1.3fc	12.9ft	1.9fc	12.9ft	2.4fc	12.9ft	2.6fc	12.9ft
32ft	0.4fc	17.1ft	0.7fc	17.1ft	1.1fc	17.1ft	1.3fc	17.1ft	1.5fc	17.1ft
40ft	0.2fc	21.4ft	0.5fc	21.4ft	0.7fc	21.4ft	0.9fc	21.4ft	0.9fc	21.4ft
48ft	0.2fc	25.7ft	0.3fc	25.7ft	0.5fc	25.7ft	0.6fc	25.7ft	0.7fc	25.7ft
60ft	0.1fc	32.2ft	0.2fc	32.2ft	0.3fc	32.2ft	0.4fc	32.2ft	0.4fc	32.2ft

At 45° Setting



POWER	15W		22W		26W		30W		33W	
DISTANCE	FOOT CANDLES	BEAM WIDTH	FOOT CANDLES	BEAM WIDTH	FOOT CANDLES	BEAM WIDTH	FOOT CANDLES	BEAM WIDTH	FOOT CANDLES	BEAM WIDTH
4ft	16.2fc	3.3ft	29.9fc	3.3ft	46.2fc	3.3ft	57.0fc	3.3ft	62.5fc	3.3ft
8ft	4.1fc	6.6ft	7.5fc	6.6ft	11.5fc	6.6ft	14.3fc	6.6ft	15.6fc	6.6ft
12ft	1.8fc	9.9ft	3.3fc	9.9ft	5.1fc	9.9ft	6.3fc	9.9ft	6.9fc	9.9ft
16ft	1.0fc	13.3ft	1.9fc	13.3ft	2.9fc	13.3ft	3.6fc	13.3ft	3.9fc	13.3ft
24ft	0.5fc	19.9ft	0.8fc	19.9ft	1.3fc	19.9ft	1.6fc	19.9ft	1.7fc	19.9ft
32ft	0.3fc	26.5ft	0.5fc	26.5ft	0.7fc	26.5ft	0.9fc	26.5ft	1.0fc	26.5ft
40ft	0.2fc	33.1ft	0.3fc	33.1ft	0.5fc	33.1ft	0.6fc	33.1ft	0.6fc	33.1ft
48ft	0.1fc	39.8ft	0.2fc	39.8ft	0.3fc	39.8ft	0.4fc	39.8ft	0.4fc	39.8ft
60ft	0.1fc	49.7ft	0.1fc	49.7ft	0.2fc	49.7ft	0.3fc	49.7ft	0.3fc	49.7ft

At 60° Setting



POWER	15W		22W		26W		30W		33W	
DISTANCE	FOOT CANDLES	BEAM WIDTH	FOOT CANDLES	BEAM WIDTH	FOOT CANDLES	BEAM WIDTH	FOOT CANDLES	BEAM WIDTH	FOOT CANDLES	BEAM WIDTH
4ft	10.6fc	4.6ft	19.5fc	4.6ft	30.1fc	4.6ft	37.1fc	4.6ft	40.7fc	4.6ft
8ft	2.6fc	9.2ft	4.9fc	9.2ft	7.5fc	9.2ft	9.3fc	9.2ft	10.2fc	9.2ft
12ft	1.2fc	13.9ft	2.2fc	13.9ft	3.3fc	13.9ft	4.1fc	13.9ft	4.5fc	13.9ft
16ft	0.7fc	18.5ft	1.2fc	18.5ft	1.9fc	18.5ft	2.3fc	18.5ft	2.5fc	18.5ft
24ft	0.3fc	27.7ft	0.5fc	27.7ft	0.8fc	27.7ft	1.0fc	27.7ft	1.1fc	27.7ft
32ft	0.2fc	37.0ft	0.3fc	37.0ft	0.5fc	37.0ft	0.6fc	37.0ft	0.6fc	37.0ft
40ft	0.1fc	46.2ft	0.2fc	46.2ft	0.3fc	46.2ft	0.4fc	46.2ft	0.4fc	46.2ft
48ft	0.1fc	55.4ft	0.1fc	55.4ft	0.2fc	55.4ft	0.3fc	55.4ft	0.3fc	55.4ft
60ft	0.0fc	69.3ft	0.1fc	69.3ft	0.1fc	69.3ft	0.2fc	69.3ft	0.2fc	69.3ft

LANDSCAPE LED LANDSCAPE

HARDSCAPE PHOTOMETRICS

7031

Mounting Height	Distance from Fixture				
	0	1'	2'	3'	4'
12"	12.73fc	2.88fc	0.42fc	0.09fc	0.03fc
24"	3.16fc	1.95fc	0.73fc	0.26fc	0.10fc
36"	1.39fc	1.11fc	0.65fc	0.33fc	0.16fc

7061

Mounting Height	Distance from Fixture				
	0	1'	2'	3'	4'
12"	36.23fc	8.55fc	1.21fc	0.28fc	0.09fc
24"	9.29fc	5.76fc	2.14fc	0.75fc	0.30fc
36"	4.18fc	3.34fc	1.86fc	0.93fc	0.47fc

7121

Mounting Height	Distance from Fixture				
	0	1'	2'	3'	4'
12"	64.85fc	15.61fc	2.42fc	0.57fc	0.19fc
24"	16.35fc	10.31fc	3.90fc	1.49fc	0.61fc
36"	7.25fc	5.85fc	3.44fc	1.77fc	0.91fc

7181

Mounting Height	Distance from Fixture				
	0	1'	2'	3'	4'
12"	90.67fc	22.67fc	3.34fc	0.76fc	0.24fc
24"	23.13fc	14.68fc	5.57fc	2.04fc	0.82fc
36"	10.31fc	8.36fc	4.83fc	2.42fc	1.21fc

DECK & PATIO PHOTOMETRICS

3011

Mounting Height	Distance from Fixture						
	0	0.5'	1'	2'	3'	4'	5'
6"	6.79fc	82fc	2.65fc	0.15fc	0.03fc	0.01fc	0.01fc
12"	15fc	39fc	9.9fc	0.42fc	0.09fc	0.03fc	0.02fc
30"	5.79fc	7.21fc	6.35fc	2.17fc	0.43fc	0.14fc	0.06fc

3021

Mounting Height	Distance from Fixture						
	0	0.5'	1'	2'	3'	4'	5'
6"	16fc	74fc	0.92fc	0.04fc	0.01fc	-	-
12"	21fc	38fc	7.29fc	0.18fc	0.03fc	0.01fc	-
30"	5.86fc	7.2fc	5.97fc	1.85fc	0.24fc	0.07fc	0.03fc


3031

Mounting Height	Distance from Fixture						
	0	0.5'	1'	2'	3'	4'	5'
6"	15fc	117fc	1.6fc	0.11fc	0.03fc	0.01fc	0.01fc
12"	15fc	43fc	19fc	0.26fc	0.07fc	0.03fc	0.01fc
30"	5.1fc	7.22fc	7fc	3.95fc	0.49fc	0.09fc	0.04fc


LANDSCAPE LED LANDSCAPE

WALL WASH PHOTOMETRICS


FIXTURE	MOUNTING DISTANCE (d)	A	B	C	D	E	F
5021-30	3ft	27.5fc	16.3fc	10.9fc	4.7fc	0.72fc	0.33fc
	4ft	15.6fc	9.6fc	5.9fc	2.7fc	0.40fc	0.18fc
	5ft	10fc	5.9fc	4.0fc	1.3fc	0.26fc	0.12fc
	6ft	6.8fc	4.1fc	2.7fc	1.2fc	0.18fc	0.08fc
	7ft	5fc	3.1fc	2.0fc	0.88fc	0.13fc	0.06fc
	8ft	3.9fc	2.4fc	1.6fc	0.67fc	0.10fc	0.05fc
	9ft	3.1fc	1.8fc	1.2fc	0.54fc	0.08fc	0.04fc
	10ft	2.5fc	1.5fc	0.99fc	0.44fc	0.06fc	0.03fc



FIXTURE	MOUNTING DISTANCE (d)	A	B	C	D	E	F
5022-30	3ft	27.5fc	16.3fc	10.9fc	4.7fc	0.72fc	0.33fc
	4ft	15.6fc	9.6fc	5.9fc	2.7fc	0.40fc	0.18fc
	5ft	10fc	5.9fc	4.0fc	1.3fc	0.26fc	0.12fc
	6ft	6.8fc	4.1fc	2.7fc	1.2fc	0.18fc	0.08fc
	7ft	5fc	3.1fc	2.0fc	0.88fc	0.13fc	0.06fc
	8ft	3.9fc	2.4fc	1.6fc	0.67fc	0.10fc	0.05fc
	9ft	3.1fc	1.8fc	1.2fc	0.54fc	0.08fc	0.04fc
	10ft	2.5fc	1.5fc	0.99fc	0.44fc	0.06fc	0.03fc



FIXTURE	MOUNTING DISTANCE (d)	A	B	C	D	E	F
5121-30	3ft	27.5fc	16.3fc	10.9fc	4.7fc	0.72fc	0.33fc
	4ft	15.6fc	9.6fc	5.9fc	2.7fc	0.40fc	0.18fc
	5ft	10fc	5.9fc	4.0fc	1.3fc	0.26fc	0.12fc
	6ft	6.8fc	4.1fc	2.7fc	1.2fc	0.18fc	0.08fc
	7ft	5fc	3.1fc	2.0fc	0.88fc	0.13fc	0.06fc
	8ft	3.9fc	2.4fc	1.6fc	0.67fc	0.10fc	0.05fc
	9ft	3.1fc	1.8fc	1.2fc	0.54fc	0.08fc	0.04fc
	10ft	2.5fc	1.5fc	0.99fc	0.44fc	0.06fc	0.03fc



Numerical index

1000-CON-PVC	32	5211	10
1011	32	5211-LSHR.....	10
1021	32	5211-SNOOT.....	10, 74
1051	32	5212	10
2000-CON-PVC	32, 34	5511	28
2011	32	6011	62
2012	32	6021	52
2021	32	6031	60
2022	32	6041	44
2031	30	6042	44
2041	40	6051	46
2051	32	6061	54
2052	32	6071	56
2061	40	6081	48
2071	34	6091	58
2081	34	6111	16
2091	34	6211	16
2101	34	6311	50
3011	38	6321	50
3021	38	6611	66
3031	38	6612	66
4011	40	6613	66
4021	40	6621	70
4031	41, 42	6622	70
4091	41	6623	70
5000-GM	12, 14, 18, 74	6631	68
5000-LCO	20	6632	68
5000-SCP	10, 12, 16, 18, 20, 44, ... 46, 48, 50, 52, 54, 56, 58, 60, 62, 74	6633	68
5000-TCL	10	6641	72
5000-TCP	10, 12, 14, 18, 20, 74	6642	72
5000-TST	12, 14, 18, 74	6643	72
5000-TST-BK.....	10	6651	64
5000-X	20	7031	8
5010-LSHR.....	10, 12, 14, 74	7061	8
5010-SNOOT.....	12, 74	7121	8
5011	12	7181	8
5011-CC	25	8000	36
5012	12, 75	8001	36
5021	20	8002	36
5021-CC	25	8003	36
5022	20, 75	8011	36
5030-GRD	24	8051	36
5030-PIP-PVC.....	24	8101	36
5031	24	9000-MTI-WT	73
5031-CC	25	9000-PCH-GY	73
5032	24, 75	9000-PCR-GY	73
5111	14	9000-SP9	10, 12, 14, 16, 18, 20, 44, 46, 48, 50, 52, 54, 56, 58, 60, 62, 74
5111-LSHR.....	16	9000-ST9	10, 12, 14, 18, 20, 44, 46, 48, 50, 52, 54, 56, 58, 60, 62, 74
5111-LSHR.....	74	9000-ST14	12, 14, 16, 18, 20, 44, 46, 48, 50, 52, 54, 56, 58, 60, 62, 74
5111-SNOOT.....	14, 74		
5121	18		

Numerical index

9020-WNT	28, 73	LENS-2X3	18, 74
9075-TRN-SS	73	LENS-2X4	20, 28, 74
9100	73	LENS-16	14, 74
9150-TRN-SS	73	LENS-20	12, 28, 74
9250	73	LENS-25	10, 24, 74
9300-TRN-SS	73		
9500	73	M	
9600-TRN-SS	73	M6000-STAK	12
		M6000-STAKE	10, 14, 20, 64, 66, 68, 70, 72
E		M6610	66
EN-2460-RB2-T	78, 79, 80	M6610-CON-KIT	66
EN-O24100-RB2-T	78, 79	M6620-CON-KIT	70
EN-OD24100-RB2-T	78	M6630-CON-KIT	68
		M6640-CON-KIT	72
F		MS-120	84, 85, 86, 89, 90
FM-W2505	91		
FM-W2510	91	P	
FM-W2605	93	PC-120	84, 85, 86, 90
FM-W2612	93	PD-W2605	93
		W	
L		WL-5105	82
LED-TCO	79	WL-5205	82
LED-TO24	36, 78	WL-LED100	40
LED-TO24-C1	36, 78, 79	WL-LED120	42
LED-TO24-C2	36, 78, 79	WL-LED130	42
LED-TO24-C3	36, 78, 79	WL-LED140	41
LED-TO24-CH5	36, 78, 79, 80	WL-LED200	40
LED-TO24-CM	79, 80	WL-LED210	41
LED-TO24-CS	79, 80	WL-LED220	42
LED-TO24-EC	36, 78, 79	WP-LED119	89
LED-TO24-IC	78	WP-LED127	89
LED-TO24-IC	79	WP-LED135	89
LED-TO24-IC6	78	WP-LED219	90
LED-TO24-IC6-RGB	79	WP-LED227	90
LED-TO24-IC12	78	WP-LED335	84
LED-TO24-IC12-RGB	79	WP-LED415	85
LED-TO24-IC72	78	WP-LED430	86
LED-TO24-IC72-RGB	79	WP-LED514	88
LED-TO24-IC120	78	WP-LED529	87
LED-TO24-IC120-RGB	79	WS-W2504	92
LED-TO24-MW	79	WS-W2505	92
LED-TO24-MW60	79	WS-W2509	92
LED-TO24-MW120	79	WS-W2510	92
LED-TO24-SW	79	WS-W2604	94
LED-TO24-SW60	79	WS-W2605	94
LED-TO24-SW120	79	WS-W2609	94
LED-TO24-WS	79, 80	WS-W2610	94
LED-TO24-X	78	WS-W20506	92
LED-TO24-X-RGB	79		
LED-TO24-Y	78		
LED-TO24-Y-RGB	78, 79		



Headquarters
Tel: 800.526.2588
Fax: 800.526.2585

East Factory
44 Harbor Park Drive
Port Washington, NY 11050

Central Factory
1600 Distribution Ct,
Lithia Springs, GA 30122

West Factory
1750 Archibald Ave
Ontario, CA 91761

Custom Orders
customs@waclighting.com
Consult with us to take advantage of our custom capabilities.

WAC LANDSCAPE LIGHTING

WAC
LANDSCAPE LIGHTING

800.526.2588 | waclandscapelighting.com

Many LED luminaire designs within contain patent pending features. WAC Lighting will not hesitate to enforce its intellectual property rights through injunctive relief and seek further relief through damages if it has reason to believe the patents are being infringed upon. WAC Lighting retains the right to modify the design of our products at any time as part of the company's continuous improvement program.

Please refer to our website for the latest product specifications. Copyright 2018