


www.capitallightingfixture.com
(800) 323-3257
(770) 965-7238
(770) 965-7254 fax

ATLANTA
5359 Rafe Banks Drive
Flowery Branch, GA 30542

DALLAS
Dallas Trade Mart
2100 Stemmons Freeway, Suite 3931TM
Dallas, TX 75207

Connect with us and stay up to date on designs, trends and special events!



CAPITAL LIGHTING FIXTURE COMPANY 2017


CAPITAL

LIGHTING FIXTURE COMPANY™

2017 Catalog



Capital Style

 2017

Copyright© 2017 Capital Lighting Fixture Company.
This catalog was printed in the U.S.A. Warranty:
Products are warranted to be free from defects in
materials and workmanship for one year from
date of sale under normal conditions of use.
LED components are warranted for five years
from date of purchase.

Hand-Painted Finishes



On-Trend
Accessories
(see our Mirror
Catalog for details)



Capital fine details

2017

Brilliant Crystals



Unique Glass
(see pages
530-533 for details)



collections

Abella NEW	12-15	Juliette	192-193	OUTDOOR	
Adele	16-17	Kingsley	194-195	Ashford	348-349
Alexander	18-25	Knox NEW	196-199	Bolton	350-351
Alisa	26-29	Leigh.....	200-203	Brookwood	352-353
Alston NEW	30-33	Loft	204-207	Carriage House.....	354-356
Arden	34-37	Lowell	208-209	Collins Hill	357
Asher	38-41	Luna	210-211	Creekside	358-361
Avanti	42-45	Manhattan NEW	212-213	Dylan	362-365
Axis	46-51	Margo.....	214-215	French Country	366-367
Bailey	52-55	Maxwell	216-217	Gentry	368-369
Barclay	56-59	Mercer NEW	218-219	Grant Park	370-371
Baxter	60-63	Mid-Century NEW	220-225	Harbour	372-373
Belmont	64-67	Midtown	226-237	Inman Park	374-376
Bennett	68-69	Milan NEW	238-241	Lakeshore	377
Berkeley	70-71	Morgan	242-245	Lanier	378-379
Blair	72-75	Nash	246-247	Main Street	380-383
Blakely	76-85	Noelle	248-249	Mission Hills	384-385
Boden	86-89	Nora	250-251	Preston	386-387
Cambridge	90-93	O'neal	252-253	Spencer	388-389
Camden NEW	94-97	Olivia	254-257	Sutter Creek	390-391
Camille	98-99	Oxford NEW	258-259	Townsende	392-393
Carlyle	100-103	Pearson	260-261	Westridge	394-395
Carrington	104-105	Perry	262-263	Assorted LED	396-397
Celine	106-109	Porter NEW	264-267	Assorted Outdoor Styles	398-399
Chandler	110-113	Ravenwood NEW	268-271		
Chapman	114-119	Regan NEW	272-277		
Charleston	120-121	Reid	278-281		
Chastain	122-125	Renaissance NEW	282-285		
Chateau	126-129	River Crest	286-289		
City NEW	130-133	Riviera	290-291	CEILING	400-417
Cole NEW	134-137	Rowan	292-295	FOYER	418-439
Corrigan	138-141	Seaton	296-299	ISLAND	440-443
Covington	142-145	Sinclair NEW	300-303	PENDANT	444-471
Dawson NEW	146-149	Stanton	304-309	PETITE	472-477
Eastman	150-151	Steele	310-313	SCONCE	478-495
Ellis	152-157	Stella	314-315	VANITY	496-531
Emery	158-159	Studio	316-319		
Everleigh	160-163	Taylor	320-321		
Fifth Avenue	164-167	Vineyard	322-323		
Fire & Ice NEW	168-171	West Port NEW	324-327		
Flynn	172-173	Westbrook	328-331		
Gavin NEW	174-177	Windsor	332-333		
Harlow	178-179	Wright NEW	334-335		
Hill House	180-183	Wyatt	336-341		
Hudson	184-185	Zander NEW	342-345		
Hutton	186-187				
Jackson	188-191				

reference

GLASS & SHADES.....	532-537
INDEX	538-546



Quality
hand-painted
finishes

2017



ABELLA-NEW
pages 12-15



ADELE
pages 16-17



ALEXANDER
pages 18-25



ALISA
pages 26-29



ALSTON-NEW
pages 30-33



ARDEN
pages 34-37



ASHER
pages 38-41



AVANTI
pages 42-45



AXIS
pages 46-51



BAILEY
pages 52-55



BARCLAY
pages 56-59



BAXTER
pages 60-63



BELMONT
pages 64-67



BENNETT
pages 68-69



BERKELEY
pages 70-71



BLAIR
pages 72-75



BLAKELY
pages 76-85



BODEN
pages 86-89



CAMBRIDGE
pages 90-93



CAMDEN-NEW
pages 94-97



CAMILLE
pages 98-99



CARLYLE
pages 100-103



CARRINGTON
pages 104-105



CELINE
pages 106-109



CHANDLER
pages 110-113



CHAPMAN
pages 114-119



CHARLESTON
pages 120-121



CHASTAIN
pages 122-125



CHATEAU
pages 126-129



CITY-NEW
pages 130-133



COLE-NEW
pages 134-137



CORRIGAN
pages 138-141



COVINGTON
pages 142-145



DAWSON-NEW
pages 146-149



EASTMAN
pages 150-151



ELLIS
pages 152-157



EMERY
pages 158-159



EVERLEIGH
pages 160-163



FIFTH AVENUE
pages 164-167



FIRE & ICE-NEW
pages 168-171



FLYNN
pages 172-173



GAVIN-NEW
pages 174-177



HARLOW
pages 178-179



HILL HOUSE
pages 180-183



HUDSON
pages 184-185



HUTTON
pages 186-187



JACKSON
pages 188-191



JULIETTE
pages 192-193



KINGSLEY
pages 194-195



KNOX-NEW
pages 196-199



LEIGH
pages 200-203



LOFT
pages 204-207



LOWELL
pages 208-209



LUNA
pages 210-211



MANHATTAN-NEW
pages 212-213




MARGO
pages 214-215



MAXWELL
pages 216-217



MERCER-NEW
pages 218-219



MID-CENTURY-NEW
pages 220-225



MIDTOWN
pages 226-237



MILAN-NEW
pages 238-241



MORGAN
pages 242-245



NASH
pages 246-247



NOELLE
pages 248-249



NORA
pages 250-251



O'NEAL
pages 252-253



OLIVIA
pages 254-257



OXFORD-NEW
pages 258-259



PEARSON
pages 260-261



PERRY
pages 262-263



PORTER-NEW
pages 264-267



RAVENWOOD-NEW
pages 268-271



REGAN-NEW
pages 272-277



REID
pages 278-281



RENAISSANCE-NEW
pages 282-285



RIVER CREST
pages 286-289



RIVIERA
pages 290-291



ROWAN
pages 292-295



SEATON
pages 296-299



SINCLAIR-NEW
pages 300-303



STANTON
pages 304-309



STEELE
pages 310-313



STELLA
pages 314-315



STUDIO
pages 316-319



TAYLOR
pages 320-321



VINEYARD
pages 322-323



WEST PORT-NEW
pages 324-327



WESTBROOK
pages 328-331



WINDSOR
pages 332-333



WRIGHT-NEW
pages 334-335



WYATT
pages 336-341



ZANDER-NEW
pages 342-345




OUTDOOR
pages 346-399



CEILING
pages 400-417



FOYER
pages 418-439



ISLAND
pages 440-443



PENDANT
pages 444-471



PETITE
pages 472-477



SCONCE
pages 478-495



VANITY
pages 496-531



GLASS
pages 532-535



SHADES
pages 536-537



CAPITAL FINISHES
see collections



COMBINATION FINISHES
see collections



abella
collection

IN CAPITAL GOLD



◀ **423081CG CHANDELIER** · *Capital Gold*
33"W x 35.50"H · Canopy: 5"W x .75"H
8 – 60 Watt E12 Candelabra · Finish: CG
Antiqued Mirror · 10' Chain; 15' Wire

▶ **623011CG SCONCE** · *Capital Gold*
6"W x 20"H x 5"E · Backplate: 6"W x 20"H x 1.50"E
Ctr/Top: 10" · 1 – 60 Watt E12 · Candelabra · Finish: CG
Antiqued Mirror · Damp Rated



CG-Capital Gold

▶ **523042CG FOYER** · *Capital Gold*
18.50"W x 28.75"H · Canopy: 5"W x .75"H · 4 – 60 Watt
E12 Candelabra · Finish: CG · Antiqued Mirror
10' Chain; 15' Wire



◀ **423041CG CHANDELIER** · *Capital Gold*
26.50"W x 28.25"H · Canopy: 5"W x .75"H · 4 – 60 Watt
E12 Candelabra · Finish: CG · Antiqued Mirror
10' Chain; 15' Wire



Coordinates With

BLAKELY
9484CG-CR PENDANT
 see page 79



2325CG CEILING
 see page 415



▲ **523041CG FOYER** · *Capital Gold*
 14.25"W x 17"H · Canopy: 5"W x .75"H · 4 – 60 Watt
 E12 Candelabra · Finish: CG · Antiqued Mirror
 10' Chain; 15' Wire



▲ **123031CG-436 VANITY** · *Capital Gold*
 24.25"W x 9.50"H x 6.75"E · Backplate: 5"W x 5"H x .75"E
 Ctr/Top: 2.50" · 3 – 100 Watt E26 Medium · Clear Beveled
 Glass · Finish: CG · Antiqued Mirror · Damp Rated



GL436 GLASS
 5.25"W x 4.50"H

◀ **4443SQ-000 PETITE** • *Silver Quartz*
18.50"W x 20"H • Canopy: 5.25"W x 1"H • 3 – 60 Watt E12
Candelabra • Finish: SQ • Wood Beads • 10' Chain; 15' Wire



adele


collection

IN SILVER QUARTZ



◀ **4444SQ CEILING** • *Silver Quartz*
16.25"W x 16"H • Canopy: 6"W x .75"H
3 – 60 Watt E12 Candelabra • Finish: SQ • Wood Beads

▶ **4442SQ-000 SCONCE** • *Silver Quartz*
10.25"W x 18"H x 5"E • Backplate: 6"W x 6"H x 1"E
Ctr/Top: 10.50" Ctr/Btm: 7.50" • 2 – 60 Watt E12
Candelabra • Finish: SQ • Wood Beads • Damp Rated





◀ **4440SQ-000 CHANDELIER** · *Silver Quartz*
32.50"W x 37.50"H · Canopy: 5.25"W x 1"H · 10 – 60 Watt
E12 Candelabra · Finish: SQ · Wood Beads · 10' Chain;
15' Wire



▶ **4446SQ-000 CHANDELIER** · *Silver Quartz*
26.50"W x 31"H · Canopy: 5.25"W x 1"H · 6 – 60 Watt
E12 Candelabra · Finish: SQ · Wood Beads · 10' Chain;
15' Wire



SQ-Silver Quartz



alexander
collection

IN BURNISHED BRONZE
& WINTER GOLD





▲ **4746WG-000 CHANDELIER** · *Winter Gold*
28.25"W x 24.75"H · Canopy: 5"W x 1"H · 6 – 60 Watt
E12 Candelabra · Finishes: BB, WG · 10' Chain; 15' Wire

▶ **4746BB-000 CHANDELIER** · *Burnished Bronze*
28.25"W x 24.75"H · Canopy: 5"W x 1"H · 6 – 60 Watt
E12 Candelabra · Finishes: BB, WG · 10' Chain; 15' Wire

Coordinates With

**LOWELL
4794TZ PENDANT**
see page 209



**EASTMAN
4884SZ PENDANT**
see page 151



BB-Burnished Bronze & WG-Winter Gold



▲ **9691WG FOYER** · *Winter Gold*
11.75"W x 19"H · Canopy: 5"W x 1"H · 4 – 60 Watt E12
Candelabra · Finishes: BB, WG · 10' Chain; 15' Wire



◀ **9691BB FOYER** · *Burnished Bronze*
11.75"W x 19"H · Canopy: 5"W x 1"H · 4 – 60 Watt E12
Candelabra · Finishes: BB, WG · 10' Chain; 15' Wire



▲ **9692BB FOYER** · *Burnished Bronze*
18.25"W x 27.50"H · Canopy: 5"W x 1"H
6 – 60 Watt E12 Candelabra · Finishes: BB, WG
10' Chain; 15' Wire

▶ **9692WG FOYER** · *Winter Gold*
18.25"W x 27.50"H · Canopy: 5"W x 1"H
6 – 60 Watt E12 Candelabra · Finishes: BB, WG
10' Chain; 15' Wire



▶ **9693WG FOYER** · *Winter Gold*

24"W x 33"H · Canopy: 5"W x 1"H · 8 – 60 Watt E12
Candelabra · Finishes: BB, WG · 10' Chain; 15' Wire



◀ **9693BB FOYER** · *Burnished Bronze*

24"W x 33"H · Canopy: 5"W x 1"H · 8 – 60 Watt E12
Candelabra · Finishes: BB, WG · 10' Chain; 15' Wire

▼ **4744WG-611 PENDANT** · *Winter Gold*

24.25"W x 46"H · 46"H overall includes 6", 12", 18"L
Removable Rods · Canopy: 5"W x 1"H · 4 – 100 Watt E26
Medium · Decorative White Fabric Shade · Frosted Glass
Diffuser with Finial · Finishes: BB, WG · 1' Chain; 6' Wire



▲ **4744BB-611 PENDANT** · *Burnished Bronze*

24.25"W x 46"H · 46"H overall includes 6", 12", 18"L
Removable Rods · Canopy: 5"W x 1"H · 4 – 100 Watt E26
Medium · Decorative White Fabric Shade · Frosted Glass
Diffuser with Finial · Finishes: BB, WG · 1' Chain; 6' Wire

▶ **4747BB-000 CHANDELIER** · *Burnished Bronze*
36"W x 25.50"H · Canopy: 5"W x 1"H · 10 – 60 Watt E12
Candelabra · Finishes: BB, WG · 10' Chain; 15' Wire



◀ **4747WG-000 CHANDELIER** · *Winter Gold*
36"W x 25.50"H · Canopy: 5"W x 1"H · 10 – 60 Watt
E12 Candelabra · Finishes: BB, WG · 10' Chain; 15' Wire



◀ **4743BB-610 CEILING** · *Burnished Bronze*
18"W x 12"H · Canopy: 5"W x 1"H · 3 – 100 Watt
E26 Medium · Decorative White Fabric Shade · Frosted
Glass Diffuser with Finial · Finishes: BB, WG · Damp
Rated



▶ **4743WG-610 CEILING** · *Winter Gold*
18"W x 12"H · Canopy: 5"W x 1"H · 3 – 100 Watt
E26 Medium · Decorative White Fabric Shade · Frosted
Glass Diffuser with Finial · Finishes: BB, WG · Damp
Rated



▶ **4748BB-000 CHANDELIER** • *Burnished Bronze*
41.25"W x 24.75"H x 23"E • Canopy: 5"W x 1"H
10 – 60 Watt E12 Candelabra • Finishes: BB, WG
10' Chain; 15' Wire



◀ **4748WG-000 CHANDELIER** • *Winter Gold*
41.25"W x 24.75"H x 23"E • Canopy: 5"W x 1"H
10 – 60 Watt E12 Candelabra • Finishes: BB, WG
10' Chain; 15' Wire



- ▶ **8071WG-LD SCONCE** · *Winter Gold*
- ▶ **8071BB-LD SCONCE** · *Burnished Bronze*

9"W x 7"H x 4"E · Backplate: 8"W x 6.75"H x .75"E
 Ctr/Top: 3.50" · Lumens: 900 · CRI > 80 · Volts/Watts:
 120V 50/60 HZ/10W · Color Temperature: 3000K
 Soft White Glass · Finishes: BB, WG
 · Damp Rated · **ADA** · [LED]



**Dimmable – LED
 Dimmer Recommended**



- ◀ **8062BB SCONCE** · *Burnished Bronze*
- ◀ **8062WG SCONCE** · *Winter Gold*

11.50"W x 11.50"H x 4"E · Mirror Backplate:
 5"W x 5"H x .75"E · Ctr/Top: 9.50" · 2 – 60 Watt E12
 Candelabra · Finishes: BB, WG · Damp Rated · **ADA**



- ▲ **8061WG SCONCE** · *Winter Gold*
- ▲ **8061BB SCONCE** · *Burnished Bronze*

5.50"W x 14"H x 4"E · Mirror Backplate:
 5"W x 14"H x .75"E · Ctr/Top: 7" Ctr/Btm: 7"
 1 – 60 Watt E12 Candelabra · Finish: BB, WG
 Damp Rated · **ADA**



▲ **8072BB-LD VANITY** · *Burnished Bronze*

27.50"W x 5.25"H x 5"E · Backplate: 26.50"W x 4.75"H x .75"E
 Ctr/Top: 2.50" · Lumens: 2700 · CRI > 80 · Volts/Watts: 120V
 50/60 HZ/10W · Color Temperature: 3000K
 White Glass · Finishes: BB, WG · Damp Rated · [LED]

Dimmable – LED
 Dimmer Recommended



▲ **8072WG-LD VANITY** · *Winter Gold*

27.50"W x 5.25"H x 5"E · Backplate: 26.50"W x 4.75"H x .75"E
 Ctr/Top: 2.50" · Lumens: 2700 · CRI > 80 · Volts/Watts: 120V
 50/60 HZ/10W · Color Temperature: 3000K
 White Glass · Finishes: BB, WG
 Damp Rated · [LED]



▲ **8073BB CEILING** · *Burnished Bronze*

16.25"W x 7.50"H · 3 – 60 Watt E26 Medium · Decorative
 White Fabric Shade · Frosted Glass Diffuser with Finial ·
 Finishes: BB, WG · Damp Rated



▲ **8073WG CEILING** · *Winter Gold*

16.25"W x 7.50"H · 3 – 60 Watt E26 Medium · Decorative
 White Fabric Shade · Frosted Glass Diffuser with Finial ·
 Finishes: BB, WG · Damp Rated



alisa
collection

IN POLISHED NICKEL



◀ **4489PN-573-CR CHANDELIER** · *Polished Nickel*
33.25"W x 32.50"H · Canopy: 5"W x 1"H · 9 – 60 Watt
E12 Candelabra · Decorative White Pleated Fabric
Stay-Straight Shades · Finish: PN · Includes Crystals
10' Chain; 15' Wire

▶ **4485PN-573-CR CHANDELIER** · *Polished Nickel*
28"W x 23.50"H · Canopy: 5"W x 1"H · 6 – 60 Watt
E12 Candelabra · Decorative White Pleated Fabric
Stay-Straight Shades · Finish: PN · Includes Crystals
10' Chain; 15' Wire





◀ **4483PN-573-CR PETITE** • *Polished Nickel*
 17"W x 19.50"H • Canopy: 5"W x 1"H • 3 – 60 Watt
 E12 Candelabra • Decorative White Pleated Fabric
 Stay-Straight Shades • Finish: PN • Includes Crystals
 4' Chain; 6' Wire

▼ **8027PN-573-CR SCONCE** • *Polished Nickel*
 12.50"W x 15.50"H x 5.75"E • Backplate: 5"W x 5"H x .75"E
 Ctr/Top: 10.25" • 2 – 60 Watt E12 Candelabra • Decorative
 White Pleated Fabric Stay-Straight Shades • Finish: PN
 Includes Crystals • Damp Rated



▶ **8026PN-573-CR SCONCE**
Polished Nickel • 5"W x 15.50"H x 5.75"E
 Backplate: 5"W x 5"H x .75"E • Ctr/Top: 7.75"
 1 – 60 Watt E12 Candelabra • Decorative
 White Pleated Fabric Stay-Straight Shade
 Finish: PN • Includes Crystals • Damp Rated



▼ **4488PN-574-CR CHANDELIER** • *Polished Nickel*
 20.50"W x 16"H • Canopy: 5"W x 1"H • 4 – 60 Watt
 E12 Candelabra • Decorative White Pleated Fabric
 Shade • Finish: PN • Includes Crystals • 4' Chain; 6' Wire



**4488PN-574-CR
 CHANDELIER**
 Includes Flush Mount Option
 20.25"W x 14.75"H



▶ **4487PN-621 ISLAND** · *Polished Nickel*
 38"W x 53.50"H x 18"E · 53.50"H Overall Includes
 6", 12" & 18"L Removable Rods · Canopy: 8.50"L x
 4.50"W x 1"H
 6 – 60 Watt E12 Candelabra · Decorative White Pleated
 Fabric · Shade · Finish: PN · Includes Crystals
 1' Chain; 6' Wire



▲ **4486PN-159 CEILING** · *Polished Nickel*
 16.25"W x 10"H · Canopy: 5"W x 1"H · 3 – 75 Watt
 E26 Medium · Milk Glass Panels · Frosted Glass
 Diffuser with Crystal Finial · Finish: PN · Includes Crystal



▲ **8021PN-127 SCONCE** · *Polished Nickel*
 5"W x 7.75"H x 6.25"E · Backplate: 5"W x 5"H x .75"E
 Ctr/Top: 3" · 1 – 75 Watt E26 Medium · Milk Glass
 Finish: PN · Includes Crystal · Damp Rated

▲ **8022PN-127 VANITY** · *Polished Nickel*
 13.50"W x 7.75"H x 6"E · Backplate: 5"W x 5"H x .75"E
 Ctr/Top: 4.75" · 2 – 75 Watt E26 Medium · Milk Glass
 Finish: PN · Includes Crystals · Damp Rated

▶ **8023PN-127 VANITY** · *Polished Nickel*
 21"W x 7.75"H x 6"E · Backplate: 5"W x 5"H x .75"E
 Ctr/Top: 3" · 3 – 75 Watt E26 Medium · Milk Glass
 Finish: PN · Includes Crystals · Damp Rated



▲ **8024PN-127 VANITY** · *Polished Nickel*
 29.25"W x 7.75"H x 6"E · Backplate: 5"W x 5"H x .75"E
 Ctr/Top: 3" · 4 – 75 Watt E26 Medium · Milk Glass
 Finish: PN · Includes Crystals · Damp Rated



alston
collection

IN OLD BRONZE



Coordinates With

213912BB-LD CEILING
see page 416




121821OB-432 VANITY
see page 519



◀ **521042OB FOYER** · *Old Bronze*
16"W x 27"H · Canopy: 5"W x .75"H · 4 – 60 Watt
E12 Candelabra · Clear Organic Glass · Finish: OB
10' Chain; 15' Wire

▶ **521041OB FOYER** · *Old Bronze*
14"W x 17"H · Canopy: 5"W x .75"H · 4 – 60 Watt
E12 Candelabra · Clear Organic Glass · Finish: OB
10' Chain; 15' Wire

**521041OB
FOYER**
Includes
Semi-Flush Option
14"W x 17.25"H



► **521043OB FOYER** • *Old Bronze*

22"W x 38"H • Canopy: 5"W x .75"H • 4 – 100 Watt E26
Medium • Clear Organic Glass • Finish: OB • 10' Chain;
15' Wire



◄ **521044OB FOYER** • *Old Bronze*


24.50"W x 16.75"H • Canopy: 5"W x .75"H • 4 – 100
Watt E26 Medium • Clear Organic Glass • Finish: OB
10' Chain; 15' Wire

**521044OB
FOYER**
Includes
Semi-Flush Option
24.50"W x 17"H




▼ **121031OB VANITY** · *Old Bronze*

24.50"W x 6.25"H x 4.75"E · Backplate: 24"W x 4.50"H x .75"E
 Ctr/Top: 4" Ctr/Btm: 2.25" · 3 – 60 Watt E12 Candelabra ·
 Clear Organic Glass · Finish: OB · Damp Rated



▼ **621013OB SCONCE** · *Old Bronze*

8"W x 12.75"H x 5.50"E · Backplate: 4.75"W x 8"H x .75"E
 Ctr/Top: 8.5" Ctr/Btm: 4.25" · 1 – 60 Watt E12 Candelabra
 Clear Organic Glass · Finish: OB · Damp Rated



▲ **621014OB SCONCE** · *Old Bronze*

9.50"W x 9.50"H x 5.50"E · Backplate: 4.75"W x 7"H x 1"E
 Ctr/Top: 5.75" Ctr/Btm: 3.75" · 1 – 60 Watt E12 Candelabra
 Clear Organic Glass · Finish: OB · Damp Rated



◀ **621012OB-654 SCONCE** · *Old Bronze*

6"W x 21.50"H x 7"E · Backplate: 5"W x 13.50"H x 1"E
 Ctr/Top: 14" Ctr/Btm: 7.5" · 1 – 60 Watt E12 Candelabra
 Decorative White Fabric Stay-Straight Shade · Finish: OB
 Damp Rated



SH654 SHADE

6"W x 4.75"H
 Stay-Straight



arden
collection
IN BRUSHED SILVER

▶ **411261BS-317 CHANDELIER** • *Brushed Silver*
29"W x 29.75"H • Canopy: 5"W x .75"H • 6 – 60 Watt E12
Candelabra • Clear Ice Glass • Finish: BS • 10' Chain; 15'
Wire



◀ **411201BS-317 CHANDELIER** • *Brushed Silver*
35"W x 37.75"H • Canopy: 5"W x .75"H • 10 – 60 Watt E12
Candelabra • Clear Ice Glass • Finish: BS • 10' Chain; 15' Wire



BS-Brushed Silver

► **311241BS-317 PENDANT** • *Brushed Silver*
14.50"W x 52"H • 52"H Overall Includes 6", 12" & 18"L
Removable Rods • Canopy: 5"W x .75"H • 4 – 60 Watt E12
Candelabra • Clear Ice Glass • Finish: BS • 1' Chain; 6' Wire



◀ **511241BS-317 FOYER** • *Brushed Silver*
15"W x 26.75"H • Canopy: 5"W x .75"H
4 – 60 Watt E12 Candelabra • Clear Ice Glass
Finish: BS • 10' Chain; 15' Wire

▼ **611211BS-317 SCONCE** • *Brushed Silver*
6"W x 18"H x 8.75"E • Backplate: 6"W x 18"H x 1"E
Ctr/Top: 10" • 1 – 60 Watt E12 Candelabra • Clear Ice Glass
Finish: BS • Damp Rated



► **111221BS-317 VANITY** • *Brushed Silver*
 15"W x 9"H x 6.75"E • Backplate: 5"W x 5"H x 1"E
 Ctr/Top: 6.50" • 2 – 60 Watt E12 Candelabra • Clear Ice Glass
 Finish: BS • Damp Rated



▲ **111231BS-317 VANITY** • *Brushed Silver*
 23.50"W x 9"H x 6.75"E • Backplate: 5"W x 5"H x 1"E
 Ctr/Top: 6.50" • 3 – 60 Watt E12 Candelabra • Clear Ice Glass
 Finish: BS • Damp Rated

▼ **111241BS-317 VANITY** • *Brushed Silver*
 32"W x 9"H x 6.75"E • Backplate: 5"W x 5"H x 1"E
 Ctr/Top: 6.50" • 4 – 60 Watt E12 Candelabra • Clear Ice Glass
 Finish: BS • Damp Rated





▲ **214931CZ-661 CEILING** · *Champagne Bronze*
15"W x 11.50"H · Canopy: 5.50"W x 2.75"H · 3 – 60 Watt
E26 Medium · Decorative White Fabric Shade · Frosted Glass
Diffuser with Finial · Finish: CZ · Damp Rated

asher

collection

IN CHAMPAGNE BRONZE

▲ **514941CZ FOYER** · *Champagne Bronze*
17"W x 29.50"H · Canopy: 5"W x 1"H · 4 – 60 Watt E12
Candelabra · Finish: CZ · K9 Crystal · 10' Chain; 15' Wire

▶ **314941CZ-662 PETITE** · *Champagne Bronze*
18.50"W x 16.75"H · Canopy: 5"W x 1"H · 4 – 60 Watt
E12 Candelabra · Decorative White Fabric Shade
Finish: CZ · K9 Crystal · 10' Chain; 15' Wire





◀ **414901CZ-660 CHANDELIER** · *Champagne Bronze*
 36"W x 38"H · Canopy: 5"W x 1"H · 10 – 60 Watt E12 Candelabra
 Decorative White Fabric Stay-Straight Shades (not shown)
 Finish: CZ · K9 Crystal · 10' Chain; 15' Wire

SH660 SHADE
 6.75"W x 4.50"H
 Stay-Straight



▶ **614911CZ-660 SCONCE** · *Champagne Bronze*
 6.75"W x 18"H x 7.75"E · Backplate: 5"W x 9.25"H x .75"E
 Ctr/Top: 13.75" · 1 – 60 Watt E12 Candelabra · Decorative White
 Fabric Stay-Straight Shade · Finish: CZ · K9 Crystal · Damp Rated



CZ-Champagne Bronze

▶ **414961CZ-660 CHANDELIER** · *Champagne Bronze*
30"W x 20"H · Canopy: 5"W x 1"H · 6 – 60 Watt E12 Candelabra
Decorative White Fabric Stay-Straight Shades · Finish: CZ · K9 Crystal
10' Chain; 15' Wire



◀ **414962CZ-660 CHANDELIER** · *Champagne Bronze*
30"W x 30"H · Canopy: 5"W x 1"H · 6 – 60 Watt E12
Candelabra · Decorative White Fabric Stay-Straight Shades (not shown)
Finish: CZ · K9 Crystal · 10' Chain; 15' Wire





◀ **114921CZ-336 VANITY** · *Champagne Bronze*
 19.25"W x 10.50"H x 7.50"E · Backplate: 5.75"W x 5.75"H x 1"E
 Ctr/Top: 2.75" Ctr/Btm: 7.75" · 2 – 100 Watt E26 Medium
 Soft White Glass · Finish: CZ · Damp Rated



▶ **114931CZ-336 VANITY** · *Champagne Bronze*
 27"W x 10.50"H x 7.50"E · Backplate: 5.75"W x 5.75"H x 1"E
 Ctr/Top: 7.75" Ctr/Btm: 2.75" · 3 – 100 Watt E26 Medium
 Soft White Glass · Finish: CZ · Damp Rated



▲ **114941CZ-336 VANITY** · *Champagne Bronze*
 36.25"W x 10.50"H x 7.50"E · Backplate: 5.75"W x 5.75"H x 1"E
 Ctr/Top: 2.75" Ctr/Btm: 7.75" · 4 – 100 Watt E26 Medium
 Soft White Glass · Finish: CZ · Damp Rated

A rustic interior hallway with a large wooden chandelier hanging from a ceiling with exposed wooden beams. A wooden door is open, leading to a bright outdoor area. A wooden bench sits on the left, and a patterned rug runs down the center of the hallway. A wooden window shutter is on the right wall.

avanti
collection

IN RUSTIC

Coordinates With

212031RT CEILING
see page 281



REID
312042RT PENDANT
see page 280



▲ **517641RT-376 FOYER** · *Rustic*
15"W x 27"H · Canopy: 5"W x 1"H · 4 – 60 Watt
E12 Candelabra · Clear Seeded Glass · Finish: RT
10' Chain; 15' Wire

▶ **517642RT-376 FOYER** · *Rustic*
22"W x 38"H · Canopy: 5"W x 1"H · 4 – 60 Watt
E12 Candelabra · Clear Seeded Glass · Finish: RT
10' Chain; 15' Wire



RT-Rustic

▶ **617611RT-376 SCONCE** · *Rustic*
 8"W x 15"H x 7.50"E · Backplate: 8"W x 8"H x 1"E
 Ctr/Top: 6" · 1 – 60 Watt E12 Candelabra · Clear Seeded
 Glass · Finish: RT · Damp Rated



◀ **117621RT-376 VANITY** · *Rustic*
 15.50"W x 13"H x 7.50"E · Backplate: 8"W x 8"H x 1"E
 Ctr/Top: 9" · 2 – 60 Watt E12 Candelabra · Clear Seeded
 Glass · Finish: RT · Damp Rated



▶ **117631RT-376 VANITY** · *Rustic*
 23"W x 13"H x 7.50"E · Backplate: 8"W x 8"H x 1"E
 Ctr/Top: 9" · 3 – 60 Watt E12 Candelabra · Clear Seeded
 Glass · Finish: RT · Damp Rated



▲ **117641RT-376 VANITY** · *Rustic*
 31"W x 13"H x 7.50"E · Backplate: 8"W x 8"H x 1"E
 Ctr/Top: 9" · 4 – 60 Watt E12 Candelabra · Clear Seeded
 Glass · Finish: RT · Damp Rated





◀ **417641RT-376 CHANDELIER** · *Rustic*
32"W x 33"H · Canopy: 5"W x 1"H · 4 – 60 Watt
E12 Candelabra · Clear Seeded Glass · Finish: RT
10' Chain; 15' Wire



◀ **817681RT-376 ISLAND** · *Rustic*
46"W x 35"H x 23.5"E · Canopy: 5"W x 1"H
8 – 60 Watt E12 Candelabra · Clear Seeded
Glass · Finish: RT · 10' Chain; 15' Wire



axis
collection

IN AGED BRASS/MATTE BLACK,
BRUSHED NICKEL, RUSSET
& WINTER GOLD

▶ **4236AB PENDANT** · *Aged Brass/Matte Black*
30"W x 30.50"H · Canopy: 5"W x 1"H · 6 – 60 Watt E12
Candelabra · Finishes: AB, BN, RS, WG · 10' Chain;
15' Wire



◀ **4234AB PENDANT** · *Aged Brass/Matte Black*
23"W x 23.50"H · Canopy: 5"W x 1"H · 4 – 60 Watt E12
Candelabra · Finishes: AB, BN, RS, WG · 10' Chain;
15' Wire

▶ **4233AB PENDANT** · *Aged Brass/Matte Black*
12.50"W x 13.25"H · Canopy: 5"W x 1"H · 3 – 60 Watt E12
Candelabra · Finishes: AB, BN, RS, WG · 10' Chain;
15' Wire





◀ **4236WG PENDANT** • *Winter Gold*
30"W x 30.50"H • Canopy: 5"W x 1"H • 6 – 60 Watt
E12 Candelabra • Finishes: AB, BN, RS, WG • 10' Chain;
15' Wire

▶ **4234WG-CR PENDANT** • *Winter Gold*
23"W x 23.50"H • Canopy: 5"W x 1"H • 4 – 60 Watt E12
Candelabra • Finishes: RS, WG • Includes Crystals
10' Chain; 15' Wire



◀ **4234WG PENDANT** • *Winter Gold*
23"W x 23.50"H • Canopy: 5"W x 1"H • 4 – 60 Watt
E12 Candelabra • Finishes: AB, BN, RS, WG • 10' Chain;
15' Wire





◀ **4236WG-CR PENDANT** • *Winter Gold*
30"W x 30.50"H • Canopy: 5"W x 1"H
6 – 60 Watt E12 Candelabra • Finishes: RS, WG
Includes Crystals • 10' Chain; 15' Wire



▲ **4233WG PENDANT** • *Winter Gold*
12.50"W x 13.25"H • Canopy: 5"W x 1"H • 3 – 60 Watt
E12 Candelabra • Finishes: AB, BN, RS, WG • 10' Chain;
15' Wire



◀ **4233WG-CR PENDANT** • *Winter Gold*
12.50"W x 13.25"H • Canopy: 5"W x 1"H • 3 – 60 Watt
E12 Candelabra • Finishes: RS, WG • Includes Crystals
10' Chain; 15' Wire

▶ **4236RS-CR PENDANT** · Russet

30"W x 30.50"H · Canopy: 5"W x 1"H · 6 – 60 Watt E12

Candelabra · Finishes: RS, WG · Includes Crystals

10' Chain; 15' Wire

▼ **4236RS PENDANT** · Russet

30"W x 30.50"H Canopy: 5"W x 1"H · 6 – 60 Watt E12

Candelabra · Finishes: AB, BN, RS, WG · 10' Chain; 15' Wire



▲ **4234RS-CR PENDANT** · Russet

23"W x 23.50"H · Canopy: 5"W x 1"H · 4 – 60 Watt E12

Candelabra · Finishes: RS, WG · Includes Crystals

10' Chain; 15' Wire

◀ **4234RS PENDANT** · Russet

23"W x 23.50"H · Canopy: 5"W x 1"H · 4 – 60 Watt

E12 Candelabra · Finishes: AB, BN, RS, WG · 10' Chain;

15' Wire

▼ **4233BN PENDANT** • *Brushed Nickel*
 12.50"W x 13.25"H • Canopy: 5"W x 1"H • 3 – 60 Watt E12
 Candelabra • Finishes: AB, BN, RS, WG • 10' Chain; 15' Wire



▲ **4233RS-CR PENDANT** • *Russet*
 12.50"W x 13.25"H • Canopy: 5"W x 1"H
 3 – 60 Watt E12 Candelabra • Finishes: RS, WG
 Includes Crystals • 10' Chain; 15' Wire

◀ **4233RS PENDANT** • *Russet*
 12.50"W x 13.25"H • Canopy: 5"W x 1"H
 3 – 60 Watt E12 Candelabra • Finishes: AB, BN,
 RS, WG • 10' Chain; 15' Wire



▲ **4234BN PENDANT** • *Brushed Nickel*
 23"W x 23.50"H • Canopy: 5"W x 1"H • 4 – 60 Watt
 E12 Candelabra • Finishes: AB, BN, RS, WG • 10' Chain;
 15' Wire

▶ **4236BN PENDANT** • *Brushed Nickel*
 30"W x 30.50"H • Canopy: 5"W x 1"H • 6 – 60 Watt
 E12 Candelabra • Finishes: AB, BN, RS, WG
 10' Chain; 15' Wire





bailey
collection

IN WINTER GOLD

▶ **4723WG PENDANT** • *Winter Gold*
15.25"W x 18.50"H • Canopy: 5"W x 1"H • 4 – 60 Watt
E12 Candelabra • Finish: WG • 10' Chain; 15' Wire



S565 SHADE
6"W x 6.50"H
Stay-Straight

◀ **4720WG-565 PENDANT** • *Winter Gold*
32"W x 34.25"H • Canopy: 5"W x 1"H • 6 – 60 Watt
E12 Candelabra • Decorative White Fabric Stay-
Straight Shades • Finish: WG • 10' Chain; 15' Wire



WG-Winter Gold



◀ **4729WG-000 CHANDELIER** · *Winter Gold*
30.75"W x 36"H · Canopy: 5"W x 1"H · 9 – 60 Watt
E12 Candelabra · Finish: WG · 10' Chain; 15' Wire



▶ **4724WG-000 CHANDELIER** · *Winter Gold*
17.50"W x 18.50"H · Canopy: 5"W x 1"H · 4 – 60 Watt
E12 Candelabra · Finish: WG · 10' Chain; 15' Wire



► **4727WG FOYER** • *Winter Gold*
12.50"W x 14.50"H • Canopy: 5"W x 1"H
3 – 60 Watt E12 Candelabra • Finish: WG
10' Chain; 15' Wire



▲ **4728WG FOYER** • *Winter Gold*
15"W x 26"H • Canopy: 5"W x 1"H • 6 – 60 Watt
E12 Candelabra • Finish: WG • 10' Chain; 15' Wire



► **4726WG-000 CHANDELIER** • *Winter Gold*
27.50"W x 30.50"H • Canopy: 5"W x 1"H • 6 – 60 Watt
E12 Candelabra • Finish: WG • 10' Chain; 15' Wire

barclay | IN CHESTERFIELD BROWN

▶ **3584CB CHANDELIER** · *Chesterfield Brown*
20.75"W x 28.50"H · Canopy: 6.25"W x 2"H · 3 – 100
Watt E26 Medium · Mist Scavo Glass · Finish: CB
10' Chain; 15' Wire



barclay
collection

IN CHESTERFIELD BROWN



▲ **3581CB-287 PENDANT** · *Chesterfield Brown*
6.25"W x 45"H · 45"H Overall Includes 6", 12"
& 18"L Removable Rods · Canopy: 6.25"W x 2.25"H
1 – 100 Watt E26 Medium · Mist Scavo Glass
Finish: CB · 1' Chain; 6' Wire

▶ **3588CB CEILING** · *Chesterfield Brown*
18"W x 18.50"H · Canopy: 6.25"W x 2"H · 2 – 100 Watt
E26 Medium · Mist Scavo Glass · Finish: CB



◀ **3585CB-287 CHANDELIER** · *Chesterfield Brown*
26"W x 28.25"H · Canopy: 6.25"W x 2"H · 5 – 100 Watt
E26 Medium · Mist Scavo Glass · Finish: CB
10' Chain; 15' Wire



G287 GLASS
6"W x 5"H
Mist Scavo

▶ **3582CB-287 CHANDELIER** · *Chesterfield Brown*
35.50"W x 40.50"H · Canopy: 6.25"W x 2"H
12 – 60 Watt E26 Medium · Mist Scavo Glass
Finish: CB · 10' Chain; 15' Wire



CB-Chesterfield Brown



◀ **3583CB-259 CHANDELIER** • *Chesterfield Brown*
25.75"W x 23"H • Canopy: 6.25"W x 2"H • 3 – 100 Watt
E26 Medium • Mist Scavo Glass • Finish: CB
10' Chain; 15' Wire

▶ **3589CB-287 CHANDELIER** • *Chesterfield Brown*
31.50"W x 36"H • Canopy: 6.25"W x 2"H • 9 – 60 Watt
E26 Medium • Mist Scavo Glass • Finish: CB
10' Chain; 15' Wire



▶ **1522CB-287 VANITY** • *Chesterfield Brown*
 20.50"W x 10"H x 9"E
 Backplate: 10"W x 5"H x 1.25"E
 Ctr/Top: 5.50" Ctr/Btm: 4.50" • 2 – 100 Watt
 E26 Medium • Mist Scavo Glass • Finish: CB
 Damp Rated



▲ **1523CB-287 VANITY** • *Chesterfield Brown*
 28.25"W x 10"H x 9"E
 Backplate: 10"W x 5"H x 1.25"E
 Ctr/Top: 5.50" Ctr/Btm: 4.50" • 3 – 100 Watt
 E26 Medium • Mist Scavo Glass • Finish: CB
 Damp Rated

▼ **1524CB-287 VANITY** • *Chesterfield Brown*
 37.50"W x 10"H x 9"E
 Backplate: 10"W x 5"H x 1.25"E
 Ctr/Top: 5.50" Ctr/Btm: 4.50" • 4 – 100 Watt
 E26 Medium • Mist Scavo Glass • Finish: CB
 Damp Rated



◀ **4551CH-128 PENDANT** • *Chrome*
6.50"W x 7"H • Canopy: 5"W x 1.25"H • 1 – 100 Watt
E26 Medium • Milk Glass • Finishes: BB, BN,
CH, PN • Gray Cord; 8' Wire

▶ **4551PN-128 PENDANT** • *Polished Nickel*
6.50"W x 7"H • Canopy: 5"W x 1.25"H • 1 – 100 Watt
E26 Medium • Milk Glass • Finishes: BB, BN,
CH, PN • Gray Cord; 8' Wire

baxter

collection

IN BRUSHED NICKEL,
BURNISHED BRONZE,
CHROME & POLISHED NICKEL

◀ **4551BN-128 PENDANT** • *Brushed Nickel*
6.50"W x 7"H • Canopy: 5"W x 1.25"H • 1 – 100 Watt
E26 Medium • Milk Glass • Finishes: BB, BN,
CH, PN • Gray Cord; 8' Wire

▶ **4551BB-128 PENDANT** • *Burnished Bronze*
6.50"W x 7"H • Canopy: 5"W x 1.25"H • 1 – 100 Watt
E26 Medium • Milk Glass • Finishes: BB, BN,
CH, PN • Black Cord; 8' Wire



◀ **4552CH-364 PENDANT** · *Chrome*

10"W x 61"H · 61"H Overall Includes 6", 12" & 18"
Removable Rods · Canopy: 5"W x 1.25"H · 1 – 100 Watt
E26 Medium · Milk Glass · Finishes: BB, BN, CH, PN
1' Chain; 6' Wire

▶ **4552PN-364 PENDANT** · *Polished Nickel*

10"W x 61"H · 61"H Overall Includes 6", 12" & 18"
Removable Rods · Canopy: 5"W x 1.25"H · 1 – 100 Watt
E26 Medium · Milk Glass · Finishes: BB, BN, CH, PN
1' Chain; 6' Wire



◀ **4552BN-364 PENDANT** · *Brushed Nickel*

10"W x 61"H · 61"H Overall Includes 6", 12" & 18"
Removable Rods · Canopy: 5"W x 1.25"H · 1 – 100
Watt E26 Medium · Milk Glass · Finishes: BB, BN,
CH, PN · 1' Chain; 6' Wire

▶ **4552BB-364 PENDANT** · *Burnished Bronze*

10"W x 61"H · 61"H Overall Includes 6", 12" & 18"
Removable Rods · Canopy: 5"W x 1.25"H · 1 – 100
Watt E26 Medium · Milk Glass · Finishes: BB, BN,
CH, PN · 1' Chain; 6' Wire





◀ **8301PN-128 SCONCE** · *Polished Nickel*
▶ **8301BB-128 SCONCE** · *Burnished Bronze*

6.50"W x 10"H x 8.25"E · Backplate: 5"W x 5"H x 1"E
Ctr/Top: 5.50" Ctr/Btm: 4.50" · 1 – 100 Watt E26
Medium · Milk Glass · Finishes: BB, BN, CH, PN
Damp Rated



◀ **8301BN-128 SCONCE** · *Brushed Nickel*
6.50"W x 10"H x 8.25"E · Backplate: 5"W x 5"H x 1"E
Ctr/Top: 5.50" Ctr/Btm: 4.50" · 1 – 100 Watt E26
Medium · Milk Glass · Finishes: BB, BN, CH, PN
Damp Rated



▲ **8301CH-128 SCONCE** · *Chrome*
6.50"W x 10"H x 8.25"E
Backplate: 5"W x 5"H x 1"E · Ctr/Top: 4.50"
Ctr/Btm: 5.50" · 1 – 100 Watt E26 Medium
Milk Glass · Finishes: BB, BN, CH, PN
Damp Rated

▶ **8302CH-128 VANITY** · *Chrome*
16.25"W x 11"H x 8"E
Backplate: 5"W x 5"H x 1"E
Ctr/Top: 4.50" Ctr/Btm: 6.50"
2 – 100 Watt E26 Medium
Milk Glass · Finishes: BB, BN,
CH, PN · Damp Rated



◀ **8302PN-128 VANITY** · *Polished Nickel*
16.25"W x 11"H x 8"E · Backplate: 5"W x 5"H x 1"E
Ctr/Top: 4.50" Ctr/Btm: 6.50" · 2 – 100 Watt E26
Medium · Milk Glass · Finishes: BB, BN, CH, PN
Damp Rated



▲ **8302BB-128 VANITY** · *Burnished Bronze*
◀ **8302BN-128 VANITY** · *Brushed Nickel*

16.25"W x 11"H x 8"E · Backplate: 5"W x 5"H x 1"E
Ctr/Top: 4.50" Ctr/Btm: 6.50" · 2 – 100 Watt E26
Medium · Milk Glass · Finishes: BB, BN, CH, PN
Damp Rated



◀ **8303CH-128 VANITY** · *Chrome*
 24.25"W x 11"H x 8.25"E
 Backplate: 5"W x 5"H x 1"E · Ctr/Top: 4.50"
 Ctr/Btm: 6.50" · 3 – 100 Watt E26 Medium
 Milk Glass · Finishes: BB, BN, CH, PN
 Damp Rated

▶ **8303PN-128 VANITY** · *Polished Nickel*
 24.25"W x 11"H x 8.25"E
 Backplate: 5"W x 5"H x 1"E · Ctr/Top: 4.50"
 Ctr/Btm: 6.50" · 3 – 100 Watt E26 Medium
 Milk Glass · Finishes: BB, BN, CH, PN
 Damp Rated



◀ **8303BN-128 VANITY** · *Brushed Nickel*
 24.25"W x 11"H x 8.25"E
 Backplate: 5"W x 5"H x 1"E · Ctr/Top: 4.50"
 Ctr/Btm: 6.50" · 3 – 100 Watt E26 Medium
 Milk Glass · Finishes: BB, BN, CH, PN
 Damp Rated

▶ **8303BB-128 VANITY** · *Burnished Bronze*
 24.25"W x 11"H x 8.25"E
 Backplate: 5"W x 5"H x 1"E · Ctr/Top: 4.50"
 Ctr/Btm: 6.50" · 3 – 100 Watt E26 Medium
 Milk Glass · Finishes: BB, BN, CH, PN
 Damp Rated





◀ **3413BB-237 CHANDELIER** • *Burnished Bronze*

Soft White Glass

▶ **3413BB-259 CHANDELIER** • *Burnished Bronze*

Mist Scavo Glass

25.50"W x 19.50"H • Canopy: 5"W x 1"H • 3 – 100 Watt

E26 Medium • Finish: BB • 10' Chain; 15' Wire



belmont

collection

IN BURNISHED BRONZE



▲ **3414BB PENDANT** • *Burnished Bronze*

Mist Scavo Glass

▶ **3414BB-SW PENDANT** • *Burnished Bronze*

Soft White Glass

18.25"W x 26"H • Canopy: 5"W x 1"H • 3 – 100 Watt

E26 Medium • Finish: BB • 10' Chain; 15' Wire



◀ **3419BB-287 CHANDELIER** · *Burnished Bronze*
31"W x 37.50"H · Canopy: 5"W x 1"H · 9 – 60 Watt E26
Medium · Mist Scavo Glass · Finish: BB · 10' Chain; 15' Wire

▼ **3419BB-242 CHANDELIER** · *Burnished Bronze*
31"W x 37.50"H · Canopy: 5"W x 1"H · 9 – 60 Watt E26
Medium · Soft White Glass · Finish: BB · 10' Chain; 15' Wire



▲ **3418BB CEILING** · *Burnished Bronze* · Mist Scavo Glass
▶ **3418BB-SW CEILING** · *Burnished Bronze* · Soft White Glass
14.50"W x 14"H · Canopy: 6"W x 2"H · 2 – 100 Watt
E26 Medium · Finish: BB






◀ **1331BB-287 SCONCE** • *Burnished Bronze* • Mist Scavo Glass
 ▶ **1331BB-242 SCONCE** • *Burnished Bronze* • Soft White Glass
 6"W x 8.50"H x 6.50"E • Backplate: 5.50"W x 8"H x 1"E
 Ctr/Top: 4.5" Ctr/Btm: 4" • 1 – 100 Watt E26 Medium • Finish: BB
 Damp Rated



◀ **3417BB ISLAND** • *Burnished Bronze*
 36"W x 24"H • Canopy: 7"L x 5.25"W x 1"H • 2 – 100
 Watt E26 Medium • Mist Scavo Glass
 Finish: BB 10' Chain; 15' Wire

▶ **3417BB-149 ISLAND** • *Burnished Bronze*
 36"W x 24"H • Canopy: 7"L x 5.25"W x 1"H • 2 – 100
 Watt E26 Medium • Soft White Glass
 Finish: BB • 10' Chain; 15' Wire



◀ **3415BB-287 CHANDELIER** • *Burnished Bronze*
 25"W x 28.50"H • Canopy: 5"W x 1"H • 5 – 100 Watt
 E26 Medium • Mist Scavo Glass • Finish: BB
 10' Chain; 15' Wire



▲ **3415BB-242 CHANDELIER** • *Burnished Bronze*
 25"W x 28.50"H • Canopy: 5"W x 1"H • 5 – 100 Watt
 E26 Medium • Soft White Glass • Finish: BB
 10' Chain; 15' Wire



▲ **1332BB-287 VANITY** • *Burnished Bronze*
 17"W x 9.50"H x 6.50"E • Backplate: 8"W x 5.50"H x 1"E
 Ctr/Top: 2.50" Ctr/Btm: 7" • 2 – 100 Watt E26 Medium
 Mist Scavo Glass • Finish: BB • Damp Rated



▲ **1332BB-242 VANITY** • *Burnished Bronze*
 17"W x 9.50"H x 6.50"E • Backplate: 8"W x 5.50"H x 1"E
 Ctr/Top: 2.50" Ctr/Btm: 7" • 2 – 100 Watt E26 Medium
 Soft White Glass • Finish: BB • Damp Rated

▶ **1333BB-287 VANITY** • *Burnished Bronze*
 25"W x 9.50"H x 6.50"E • Backplate: 8"W x 5.50"H x 1"E
 Ctr/Top: 2.50" Ctr/Btm: 7" • 3 – 100 Watt E26 Medium
 Mist Scavo Glass • Finish: BB • Damp Rated



◀ **1333BB-242 VANITY** • *Burnished Bronze*
 25"W x 9.50"H x 6.50"E • Backplate: 8"W x 5.50"H x 1"E
 Ctr/Top: 2.50" Ctr/Btm: 7" • 3 – 100 Watt E26 Medium
 Soft White Glass • Finish: BB • Damp Rated



G287 GLASS
 6"W x 5"H
 Mist Scavo



▶ **1334BB-287 VANITY** • *Burnished Bronze*
 34"W x 9.50"H x 6.50"E • Backplate: 8"W x 5.50"H x 1"E
 Ctr/Top: 2.50" Ctr/Btm: 7" • 4 – 100 Watt E26 Medium
 Mist Scavo Glass • Finish: BB • Damp Rated



G242 GLASS
 6"W x 5"H
 Soft White



▶ **1334BB-242 VANITY** • *Burnished Bronze*
 34"W x 9.50"H x 6.50"E • Backplate: 8"W x 5.50"H x 1"E
 Ctr/Top: 2.50" Ctr/Btm: 7" • 4 – 100 Watt E26 Medium
 Soft White Glass • Finish: BB • Damp Rated

▶ **61111RS-653 SCONCE** · *Russet*
6.75"W x 17.50"H x 8.25"E
Backplate: 5"W x 10"H x .75"E · Ctr/Top: 11"
Ctr/Btm: 6.50" · 1 – 60 Watt E12 Round · Mesh
Stay-Straight Shade · Finish: RS · Damp Rated

bennett

collection

IN RUSSET



▲ **311131RS-664 PENDANT** · *Russet*
14.75"W x 61"H · 61"H Overall Includes 6", 12" & 18"L
Removable Rods · Canopy: 5"W x .75"H · 3 – 60 Watt
E12 Candelabra · Mesh Stay-Straight Shade · Finish: RS
1' Chain; 6' Wire

▶ **511141RS-665 FOYER** · *Russet*
15"W x 24.25"H · Canopy: 5"W x .75"H
4 – 60 Watt E12 Candelabra · Mesh
Stay-Straight Shade · Finish: RS
10' Chain; 15' Wire



◀ **41110IRS-653 CHANDELIER** • *Russet*
 36"W x 33"H • Canopy: 5"W x .75"H • 10 – 60 Watt
 E12 Round • Mesh Stay-Straight Shades • Finish: RS
 10' Chain; 15' Wire

▶ **41116IRS-653 CHANDELIER** • *Russet*
 28.25"W x 23.50"H • Canopy: 5"W x .75"H
 6 – 60 Watt E12 Round • Mesh Stay-Straight Shades
 Finish: RS • 10' Chain; 15' Wire



SH653 SHADE
 6.5"W x 4"H
 Mesh Stay-Straight



RS-Russet





▼ **8532WG-300 VANITY** · *Winter Gold*

13.75"W x 8"H x 6.75"E

Backplate: 6.50"W x 4.50"H x .75"E

Ctr/Top: 2" Ctr/Btm: 6" · 2 – 100 Watt E26

Medium · Milk Glass · Finish: WG · Damp Rated

▲ **8533WG-300 VANITY** · *Winter Gold*

20.75"W x 8"H x 7.50"E

Backplate: 6.50"W x 4.50"H x .75"E

Ctr/Top: 2" Ctr/Btm: 6" · 3 – 100 Watt E26

Medium · Milk Glass · Finish: WG · Damp Rated



G300 GLASS
5.5"W x 5.5"H



berkeley
collection

IN WINTER GOLD



▲ **8534WG-300 VANITY** · *Winter Gold*

29.50"W x 8"H x 7.50"E

Backplate: 6.50"W x 4.50"H x .75"E · Ctr/Top: 2"

Ctr/Btm: 6" · 4 – 100 Watt E26 Medium · Milk Glass

Finish: WG · Damp Rated

▲ **4961WG-000 SCONCE** · *Winter Gold*

4.50"W x 14.50"H x 4"E

Backplate: 4.50"W x 6.50"H x .75"E

Ctr/Top: 3.25" Ctr/Btm: 11.25"

1 – 60 Watt E12 Candelabra · Finish: WG

Includes Metal & Crystal Adornments

Damp Rated · **ADA**



◀ **4960WG-000 CHANDELIER** • *Winter Gold*
 33"W x 40.50"H • Canopy: 5.25"W x 1"H • 10 – 60 Watt
 E12 Candelabra • Finish: WG • Includes Metal & Crystal
 Adornments • 10' Chain; 15' Wire



▼ **4966WG-000 CHANDELIER** • *Winter Gold*
 28.75"W x 33.25"H • Canopy: 5"W x 1"H • 6 – 60 Watt
 E12 Candelabra • Finish: WG • Includes Metal & Crystal
 Adornments • 10' Chain; 15' Wire



**4964WG-617
 PENDANT**
 Includes Flush
 Mount Option
 21.50"W x 19.50"H



◀ **4964WG-617 PENDANT** • *Winter Gold*
 21.50"W x 55.50"H • 55.50"H Overall Includes 6", 12"
 & 18"L Removable Rods • Canopy: 5"W x 1"H • 4 – 100
 Watt E26 Medium • Decorative White Fabric Shade •
 Frosted Glass Diffuser • Finish: WG
 Includes Metal & Crystal Adornments • 1' Chain; 6' Wire



WG-Winter Gold



blair
collection

IN ANTIQUE SILVER





▲ **4940AS-000 CHANDELIER** • *Antique Silver*
33.25"W x 34.50"H • Canopy: 7"W x 1.50"H • 10 – 60
Watt E12 Candelabra • Finish: AS • 10' Chain; 15' Wire

▶ **4946AS-000 CHANDELIER** • *Antique Silver*
26.25"W x 28.50"H • Canopy: 5"W x 1"H • 6 – 60 Watt
E12 Candelabra • Finish: AS • 10' Chain; 15' Wire



AS-Antique Silver

Coordinates With

BLAKELY
9484AS-CR PENDANT
see page 79



CORRIGAN
310961AS PENDANT
see page 141





◀ **4942AS-636 SCONCE** • *Antique Silver*
12.50"W x 10"H x 5.50"E
Backplate: 12.50"W x 5.50"H x 1.25"E
Ctr/Top: 2.75" Ctr/Btm: 7.5" • 2 – 60 Watt E12
Candelabra • Decorative White Fabric Shade
Finish: AS • Damp Rated



▶ **4941AS-635 SCONCE** • *Antique Silver*
10"W x 18.75"H x 5.25"E
Backplate: 7.25"W x 10"H x 1"H • Ctr/Top: 3.75"
Ctr/Btm: 15.25" • 1 – 60 Watt E12 Candelabra
Decorative White Fabric Shade • Finish: AS
Damp Rated



◀ **9896AS FOYER** • *Antique Silver*
18"W x 34"H • Canopy: 5"W x 1"H • 6 – 60 Watt
E12 Candelabra • Finish: AS • 10' Chain; 15' Wire



▲ **9894AS FOYER** • *Antique Silver*
12"W x 18.50"H • Canopy: 5"W x 1"H
4 – 60 Watt E12 Candelabra • Finish: AS
10' Chain; 15' Wire

► **8551AS-299 SCONCE** • *Antique Silver*

5.25"W x 9.50"H x 6.75"E • Backplate: 4.75"W x 8.50"H x 1"E
 Ctr/Top: 5.50" Ctr/Btm: 4" • 1 – 100 Watt E26 Medium
 Soft White Glass • Finish: AS • Damp Rated



◄ **8552AS-299 VANITY** • *Antique Silver*

17.75"W x 9"H x 6.75"E • Backplate: 8.50"W x 4.75"H x 1"E
 Ctr/Top: 2.50" Ctr/Btm: 6.50" • 2 – 100 Watt E26 Medium
 Soft White Glass • Finish: AS • Damp Rated



G299 GLASS
 5.25"W x 4.75"H

► **8553AS-299 VANITY** • *Antique Silver*

20"W x 9.25"H x 7"E • Backplate: 8.50"W x 4.75"H x 1"E
 Ctr/Top: 2.75" Ctr/Btm: 6.50" • 3 – 100 Watt E26
 Medium • Soft White Glass • Finish: AS • Damp Rated



▲ **8554AS-299 VANITY** • *Antique Silver*

27"W x 9"H x 7.25"E • Backplate: 8.50"W x 4.75"H x 1"E
 Ctr/Top: 2.75" Ctr/Btm: 6.50" • 4 – 100 Watt E26
 Medium • Soft White Glass • Finish: AS • Damp Rated



blakely

collection

IN ANTIQUE GOLD,
ANTIQUÉ SILVER &
CAPITAL GOLD



◀ **4180AS-CR CHANDELIER** • *Antique Silver*
32"W x 38.75"H • Canopy: 5.25"W x 1.25"H • 10 – 60 Watt
E12 Candelabra • Finishes: AG, AS, CG • Clear Crystals
10' Chain; 15' Wire



▲ **4180CG-CR CHANDELIER** • *Capital Gold*
32"W x 38.75"H • Canopy: 5.25"W x 1.25"H • 10 – 60 Watt
E12 Candelabra • Finishes: AG, AS, CG • Clear Crystals
10' Chain; 15' Wire



◀ **4180AG-CR CHANDELIER** • *Antique Gold*
32"W x 38.75"H • Canopy: 5.25"W x 1.25"H •
10 – 60 Watt E12 Candelabra • Finishes: AG, AS, CG •
Clear Crystals • 10' Chain; 15' Wire

▶ **4186CG-CR CHANDELIER** · *Capital Gold*

▼ **4186AG-CR CHANDELIER** · *Antique Gold*

27.50"W x 31.75"H · Canopy: 5.25"W x 1.25"H
6 – 60 Watt E12 Candelabra · Finishes: AG, AS, CG
Clear Crystals · 10' Chain; 15' Wire



▶ **4186AS-CR CHANDELIER** · *Antique Silver*

27.50"W x 31.75"H · Canopy: 5.25"W x 1.25"H

6 – 60 Watt E12 Candelabra

Finishes: AG, AS, CG · Clear Crystals

10' Chain; 15' Wire



▲ **1616AG-CR SCONCE** · *Antique Gold*

▲ **1616AS-CR SCONCE** · *Antique Silver*

▶ **1616CG-CR SCONCE** · *Capital Gold*

5"W x 13.25"H x 4.25"E

Backplate: 5"W x 7.25"H x 1.25"E · Ctr/Top: 5.25"

Ctr/Btm: 8" · 1 – 60 Watt E12 Candelabra · Finishes:

AG, AS, CG · Clear Crystals · Damp Rated



- ◀ 4184AG-CR PETITE · *Antique Gold*
- ◀ 4184AS-CR PETITE · *Antique Silver*
- ▲ 4184CG-CR PETITE · *Capital Gold*

18"W x 21.50"H · Canopy: 5.25"W x 1.25"H
4 – 60 Watt E12 Candelabra · Finishes: AG, AS, CG
Clear Crystals · 10' Chain; 15' Wire



- ▲ 9484AG-CR PENDANT · *Antique Gold*
- ▲ 9484AS-CR PENDANT · *Antique Silver*
- ▶ 9484CG-CR PENDANT · *Capital Gold*

15"W x 16.50"H · Canopy: 5.25"W x 1.25"H
4 – 60 Watt E12 Candelabra · Finishes: AG, AS, CG
Clear Crystals · 10' Chain; 15' Wire



9481AS FOYER
Includes Flush
Mount Option
12.25"W x 16.75"H



9481AS-CR FOYER
Includes Flush
Mount Option
12.25"W x 16.75"H



▲ **9481AS FOYER** · *Antique Silver*
▲ **9481AS-CR FOYER** · *Antique Silver* · Clear Crystals
12.25"W x 17.75"H · Canopy: 5.25"W x 1.25"H
3 – 60 Watt E12 Candelabra · Finishes: AG, AS, CG
Includes Flush Mount Option · 10' Chain; 15' Wire



▲ **9481AG FOYER** · *Antique Gold*
▲ **9481AG-CR FOYER** · *Antique Gold* · Clear Crystals

12.25"W x 17.75"H · Canopy: 5.25"W x 1.25"H · 3 – 60 Watt
E12 Candelabra · Finishes: AG, AS, CG · 10' Chain; 15' Wire



9481CG-CR FOYER
Includes Flush
Mount Option
12.25"W x 16.75"H



9481CG FOYER
Includes Flush
Mount Option
12.25"W x 16.75"H



▲ **9481CG FOYER** · *Capital Gold*
▲ **9481CG-CR FOYER** · *Capital Gold* · Clear Crystals
12.25"W x 17.75"H · Canopy: 5.25"W x 1.25"H
3 – 60 Watt E12 Candelabra · Finishes: AG, AS, CG
Includes Flush Mount Option · 10' Chain; 15' Wire

- ▶ **9482AG FOYER** · *Antique Gold*
- ▶ **9482AG-CR FOYER** · *Antique Gold* · Clear Crystals

18"W x 29"H · Canopy: 5.25"W x 1.25"H
4 – 60 Watt E12 Candelabra · Finishes: AG,
AS, CG · 10' Chain; 15' Wire



- ▼ **9482AS FOYER** · *Antique Silver*
- ▼ **9482AS-CR FOYER** · *Antique Silver* · Clear Crystals

18"W x 29"H · Canopy: 5.25"W x 1.25"H
4 – 60 Watt E12 Candelabra · Finishes: AG,
AS, CG · 10' Chain; 15' Wire



- ▲ **1617AG-CR SCONCE** · *Antique Gold*
- ▲ **1617AS-CR SCONCE** · *Antique Silver*
- ▲ **1617CG-CR SCONCE** · *Capital Gold*

7"W x 12.50"H x 4.25"E
Backplate: 5"W x 7.25"H x 1.25"E
Ctr/Top: 5.25" Ctr/Btm: 8" · 2 – 60 Watt E12
Candelabra · Finishes: AG, AS, CG · Clear Crystals
Damp Rated



- ◀ **9482CG FOYER** · *Capital Gold*
- ◀ **9482CG-CR FOYER** · *Capital Gold* · Clear Crystals

18"W x 29"H · Canopy: 5.25"W x 1.25"H
4 – 60 Watt E12 Candelabra · Finishes: AG,
AS, CG · 10' Chain; 15' Wire



◀ **9483AG FOYER** • *Antique Gold*

◀ **9483AG-CR FOYER** • *Antique Gold* • Clear Crystals
22.50"W x 36.50"H • Canopy: 5.25"W x 1.25"H
6 – 60 Watt E12 Candelabra • Finishes: AG, AS,
CG • 10' Chain; 15' Wire

▶ **9483AS FOYER** • *Antique Silver*

22.50"W x 36.50"H • Canopy: 5.25"W x 1.25"H
6 – 60 Watt E12 Candelabra • Finishes: AG, AS,
CG • 10' Chain; 15' Wire



▲ **9483AS-CR FOYER** • *Antique Silver*

22.50"W x 36.50"H • Canopy: 5.25"W x 1.25"H
6 – 60 Watt E12 Candelabra • Finishes: AG, AS,
CG • Clear Crystals • 10' Chain; 15' Wire



◀ **9483CG FOYER** • *Capital Gold*

22.50"W x 36.50"H • Canopy: 5.25"W x 1.25"H
6 – 60 Watt E12 Candelabra • Finishes: AG, AS,
CG • 10' Chain; 15' Wire

▶ **9483CG-CR FOYER** • *Capital Gold*

22.50"W x 36.50"H • Canopy: 5.25"W x 1.25"H
6 – 60 Watt E12 Candelabra • Finishes: AG, AS,
CG • Clear Crystals • 10' Chain; 15' Wire



- ▶ **8523AG-114 VANITY** · *Antique Gold*
- ▼ **8523CG-114 VANITY** · *Capital Gold*

24.25"W x 8.75"H x 7.75"E
 Backplate: 7.25"W x 5"H x 1"E
 Ctr/Top: 2.50" Ctr/Btm: 6.25" · 3 – 75 Watt E26 Medium
 Soft White Glass · Finishes: AG, AS, CG · Damp Rated



- ◀ **8522AS-114 VANITY** · *Antique Silver*
- 15.75"W x 8.75"H x 7.75"E
 Backplate: 7.25"W x 5"H x 1"E
 Ctr/Top: 2.50" Ctr/Btm: 6.25" · 2 – 75 Watt E26 Medium
 Soft White Glass · Finish: AS · Damp Rated

- ▶ **8523AS-114 VANITY** · *Antique Silver*
- 24.25"W x 8.75"H x 7.75"E
 Backplate: 7.25"W x 5"H x 1"E
 Ctr/Top: 2.50" Ctr/Btm: 6.25"
 3 – 75 Watt E26 Medium
 Soft White Glass · Finishes: AG, AS, CG
 Damp Rated



- ▶ **8524AS-114 VANITY** · *Antique Silver*
- 33"W x 8.75"H x 7.75"E
 Backplate: 7.25"W x 5"H x 1"E
 Ctr/Top: 2.50" Ctr/Btm: 6.25"
 4 – 75 Watt E26 Medium
 Soft White Glass · Finish: AS
 Damp Rated





- ◀ 8521CG-CR SCONCE · *Capital Gold*
- ◀ 8521AG-CR SCONCE · *Antique Gold*
- ▶ 8521AS-CR SCONCE · *Antique Silver*

5"W x 7.75"H x 6"E
 Backplate: 5"W x 7.25"H x 1"E · Ctr/Top: 4"
 Ctr/Btm: 3.75" · 1 – 60 Watt E26 Medium
 Finishes: AG, AS, CG · Clear Crystals
 Damp Rated



- ◀ 8522CG-CR VANITY · *Capital Gold*
- ◀ 8522AG-CR VANITY · *Antique Gold*
- ▶ 8522AS-CR VANITY · *Antique Silver*

12"W x 10"H x 6"E
 Backplate: 7.25"W x 5"H x 1"E
 Ctr/Top: 2.50" Ctr/Btm: 7.50" · 2 – 60 Watt
 E26 Medium · Finishes: AG, AS, CG
 Clear Crystals · Damp Rated



- ▲ 8528AG-CR VANITY · *Antique Gold*
- ▲ 8528AS-CR VANITY · *Antique Silver*
- ◀ 8528CG-CR VANITY · *Capital Gold*

18.50"W x 9.50"H x 6"E
 Backplate: 7.25"W x 5"H x 1"E
 Ctr/Top: 2.50" Ctr/Btm: 7" · 3 – 60 Watt
 E26 Medium · Finishes: AG, AS, CG
 Clear Crystals · Damp Rated





◀ **8523AG-CR VANITY** · *Antique Gold*
 ▼ **8523AS-CR VANITY** · *Antique Silver*

20.50"W x 10"H x 6"E
 Backplate: 7.25"W x 5"H x 1"E · Ctr/Top: 2.50"
 Ctr/Btm: 7.50" · 3 – 60 Watt E26 Medium · Finishes:
 AG, AS, CG · Clear Crystals · Damp Rated



◀ **8523CG-CR VANITY** · *Capital Gold*

20.50"W x 10"H x 6"E
 Backplate: 7.25"W x 5"H x 1"E · Ctr/Top: 2.50"
 Ctr/Btm: 7.50" · 3 – 60 Watt E26 Medium · Finishes:
 AG, AS, CG · Clear Crystals · Damp Rated



◀ **8524AG-CR VANITY**
Antique Gold · 29.50"W x 10"H x 6"E

Backplate: 7.25"W x 5"H x 1"E
 Ctr/Top: 2.50" Ctr/Btm: 7.50"
 4 – 60 Watt E26 Medium · Clear Crystals
 Finishes: AG, AS, CG · Damp Rated

▶ **8524AS-CR VANITY** · *Antique Silver*
 ▶ **8524CG-CR VANITY** · *Capital Gold*

29.50"W x 10"H x 6"E
 Backplate: 7.25"W x 5"H x 1"E
 Ctr/Top: 2.50" Ctr/Btm: 7.50"
 4 – 60 Watt E26 Medium · Clear Crystals
 Finishes: AG, AS, CG · Damp Rated





boden

collection

IN BRUSHED NICKEL
BURNISHED BRONZE,
& SOFT GOLD



◀ **412361BN-324 CHANDELIER** · *Brushed Nickel*
 32.75"W x 27"H · Canopy: 5"W x 1"H · 6 – 100 Watt
 E26 Medium · Soft White Glass · Finishes: BB, BN
 10' Chain; 15' Wire

▼ **412361BB-324 CHANDELIER** · *Burnished Bronze*
 32.75"W x 27"H · Canopy: 5"W x 1"H · 6 – 100 Watt
 E26 Medium · Soft White Glass · Finishes: BB, BN
 10' Chain; 15' Wire



▲ **612311BN-324 SCONCE** · *Brushed Nickel*
 5"W x 15.25"H x 8.50"E
 Backplate: 5"W x 15.25"H x 1"E · Ctr/Top: 7.50"
 Ctr/Btm: 7.75" · 1 – 100 Watt E26 Medium
 Soft White Glass · Finishes: BB, BN
 Damp Rated



◀ **612311BB-324 SCONCE** · *Burnished Bronze*
 5"W x 15.25"H x 8.50"E
 Backplate: 5"W x 15.25"H x 1"E · Ctr/Top: 7.50"
 Ctr/Btm: 7.75" · 1 – 100 Watt E26 Medium
 Soft White Glass · Finishes: BB, BN
 Damp Rated



◀ **512341BB FOYER** · *Burnished Bronze*
 18.75"W x 30"H · Canopy: 5"W x .75"H
 4 – 60 Watt E12 Candelabra
 Finishes: BB, BN · 10' Chain; 15' Wire

▶ **512341BN FOYER** · *Brushed Nickel*
 18.75"W x 30"H · Canopy: 5"W x .75"H
 4 – 60 Watt E12 Candelabra
 Finishes: BB, BN · 10' Chain; 15' Wire



▲ **112321SF-324 VANITY** · *Soft Gold*
 ▶ **112321BN-324 VANITY** · *Brushed Nickel*
 ▶ **112321BB-324 VANITY** · *Burnished Bronze*

14"W x 10.50"H x 6"E · Backplate: 11"W x 5"H x 1"E
 Ctr/Top: 2.50" Ctr/Btm: 8" · 2 – 100 Watt E26 Medium
 Soft White Glass · Finishes: BB, BN, SF · Damp Rated





- ▲ 112331SF-324 VANITY • *Soft Gold*
- ▲ 112331BN-324 VANITY • *Brushed Nickel*
- ◀ 112331BB-324 VANITY • *Burnished Bronze*

23"W x 10.50"H x 6"E
 Backplate: 11"W x 5"H x 1"E • Ctr/Top: 2.50"
 Ctr/Btm: 8" • 3 – 100 Watt E26 Medium • Soft White
 Glass • Finishes: BB, BN, SF • Damp Rated



- ▶ 112341SF-324 VANITY
Soft Gold
- ▶ 112341BN-324 VANITY
Brushed Nickel
- ▶ 112341BB-324 VANITY
Burnished Bronze

32"W x 10.50"H x 6"E
 Backplate: 15"W x 5"H x 1"E
 Ctr/Top: 2.50" Ctr/Btm: 8"
 4 – 100 Watt E26 Medium
 Soft White Glass
 Finishes: BB, BN, SF
 Damp Rated





cambridge
collection

IN WINTER GOLD



◀ **413662WG CHANDELIER** · *Winter Gold*
27"W x 35"H · Canopy: 5"W x 1"H · 6 – 60 Watt
E12 Candelabra · Finish: WG · Includes Crystals
10' Chain; 15' Wire

▶ **413602WG CHANDELIER** · *Winter Gold*
49.50"W x 62"H · Canopy: 5"W x 1"H · 16 – 60 Watt E12
Candelabra · Finish: WG · Includes Crystals
10' Chain; 15' Wire



WG-Winter Gold



◀ **613611WG SCONCE** • *Winter Gold*
5"W x 22.50"H x 6.50"E • Mirror Backplate:
5"W x 15"H • x .75"E • Ctr/Top: 11.50" Ctr/Btm: 11"
1 – 60 Watt E12 Candelabra • Finish: WG
Includes Crystals • Damp Rated

▶ **513641WG FOYER** • *Winter Gold*
16"W x 31"H • Canopy: 5"W x 1"H
4 – 60 Watt E12 Candelabra • Finish: WG
Includes Crystals • 10' Chain; 15' Wire



◀ **413661WG CHANDELIER** • *Winter Gold*
29"W x 21"H • Canopy: 5"W x 1"H • 6 – 60 Watt E12
Candelabra • Finish: WG • Includes Crystals • 10' Chain;
15' Wire



PERFECT FOR LOW CEILINGS!



◀ **313641WG PETITE** · *Winter Gold*
16"W x 21.50"H · Canopy: 5"W x 1"H · 4 – 60 Watt
E12 Candelabra · Finish: WG · Includes Crystals
10' Chain; 15' Wire

▶ **413601WG CHANDELIER** · *Winter Gold*
33.75"W x 44.50"H · Canopy: 5"W x 1"H · 10 – 60 Watt
E12 Candelabra · Finish: WG · Includes Crystals
10' Chain; 15' Wire





camden
collection

IN POLISHED NICKEL



◀ **421661PN-423 CHANDELIER** • *Polished Nickel*
29.75"W x 27.50"H • Canopy: 5"W x .75"H • 6 – 100
Watt E26 Medium • Clear Beveled Glass • Finish: PN
10' Chain; 15' Wire

Coordinates With

PERRY
4864PN PENDANT
see page 263



HUDSON
611911PN SCONCE
see page 185



214141PN CEILING
see page 411






▲ **120741PN-423 VANITY** · *Polished Nickel*
33.25"W x 9.25"H x 6.50"E · Backplate: 8"W x 5"H x 1"E
Ctr/Top: 2.50" Ctr/Btm: 6.75" · 4 – 100 Watt E26
Medium · Clear Beveled Glass · Finish: PN · Damp Rated

▼ **120731PN-423 VANITY** · *Polished Nickel*
23.50"W x 9.25"H x 6.50"E · Backplate: 8"W x 5"H x 1"E
Ctr/Top: 6.75" Ctr/Btm: 2.50" · 3 – 100 Watt E26
Medium · Clear Beveled Glass · Finish: PN · Damp Rated



◀ **120721PN-423 VANITY** · *Polished Nickel*
13.75"W x 9.25"H x 6.50"E · Backplate: 8"W x 5"H x 1"E
Ctr/Top: 2.50" Ctr/Btm: 6.75" · 2 – 100 Watt E26
Medium · Clear Beveled Glass · Finish: PN · Damp Rated

► **421601PN-423 CHANDELIER** · *Polished Nickel*
36"W x 38.25"H · Canopy: 5"W x .75"H · 10 – 100 Watt
E26 Medium · Clear Beveled Glass · Finish: PN
10' Chain; 15' Wire



GL423
4"W x 6.25"H



camille
collection
IN SOFT GOLD





▲ **310731SF PENDANT** · *Soft Gold*
 13.50"W x 16.25"H · Canopy: 5"W x 1"H
 3 – 60 Watt E12 Candelabra · Finish: SF
 K9 Crystals · 10' Chain; 15' Wire

▶ **310741SF PENDANT** · *Soft Gold*
 18.75"W x 21"H · Canopy: 5"W x 1"H · 4 – 60 Watt E12
 Candelabra · Finish: SF · K9 Crystals · 10' Chain; 15' Wire



Coordinates With

<p>MERCER 621212WG-654 SCONCE see page 219</p> 	<p>NOELLE 412661WG-654 CHANDELIER see page 248</p> 
--	--



◀ **210731SF CEILING** · *Soft Gold*
 15.25"W x 12.50"H · Canopy: 5"W x 1"H · 3 – 60 Watt
 E12 Candelabra · Finish: SF · K9 Crystals



SF-Soft Gold




carlyle
collection

IN GILDED SILVER



◀ **411761GS-654 CHANDELIER** • *Gilded Silver*
27.50"W x 21.50"H • Canopy: 5"W x 1"H
6 – 60 Watt E12 Candelabra • Decorative White
Fabric Stay-Straight Shades • Finish: GS
Clear Glass Adornments • 10' Chain; 15' Wire

▶ **411701GS-654 CHANDELIER** • *Gilded Silver*
33.50"W x 37.25"H • Canopy: 5"W x 1"H
10 – 60 Watt E12 Candelabra • Decorative White
Fabric Stay-Straight Shades • Finish: GS
Clear Glass Adornments • 10' Chain; 15' Wire



GS-Gilded Silver

► **611711GS-654 SCONCE** · *Gilded Silver*
6"W x 20.25"H x 7.75"E · Mirror Backplate:
5"W x 8"H x .75"E · Ctr/Top: 10" Ctr/Btm: 10.25"
1 – 60 Watt E12 Candelabra · Decorative White
Fabric Stay-Straight Shade · Finish: GS · Clear Glass
Adornment · Damp Rated



◄ **511741GS FOYER** · *Gilded Silver*
15.25"W x 26.50"H · Canopy: 5"W x .75"H
4 – 60 Watt E12 Candelabra · Finish: GS
Clear Glass Adornments · 10' Chain; 15' Wire



◀ **111721GS-352 VANITY** • *Gilded Silver*
 15"W x 7.25"H x 7"E
 Backplate: 5"W x 5"H x .75"E • Ctr/Top: 4.75"
 Ctr/Btm: 2.50" • 2 – 100 Watt E26 Medium
 Milk Glass • Finish: GS • Damp Rated



GL352 GLASS
 5.50"W x 5"H



▲ **111731GS-352 VANITY** • *Gilded Silver*
 24"W x 7.25"H x 7"E • Backplate: 5"W x 5"H x .75"E
 Ctr/Top: 2.50" Ctr/Btm: 4.75" • 3 – 100 Watt E26
 Medium • Milk Glass • Finish: GS • Damp Rated



▲ **111741GS-352 VANITY** • *Gilded Silver*
 32.75"W x 7.25"H x 7"E • Backplate: 5"W x 5"H x .75"E
 Ctr/Top: 2.50" Ctr/Btm: 4.75" • 4 – 100 Watt E26
 Medium • Milk Glass • Finish: GS • Damp Rated



carrington
collection

IN POLISHED NICKEL
& WINTER GOLD



◀ **7025PN-CR CHANDELIER** · *Polished Nickel*
30.25"W x 34.50"H · Canopy: 5"W x 1"H
6 – 60 Watt E12 Candelabra · Finish: PN
Includes Clear Crystals · 10' Chain; 15' Wire

**7023PN-CR
CHANDELIER**
Includes
Semi-Flush Option
22.50"W x 26"H



▲ **7023PN-CR CHANDELIER** · *Polished Nickel*
22.50"W x 27"H · Canopy: 5"W x 1"H
6 – 60 Watt E12 Candelabra · Finish: PN
Includes Clear Crystals · 10' Chain; 15' Wire



◀ **3184WG-CR PENDANT** · *Winter Gold*
24.75"W x 62"H · 62"H Overall Includes 6", 12" & 18"L
Removable Rods · Canopy: 5"W x 1"H
4 – 60 Watt E12 Candelabra · Finish: WG
Includes Clear Crystals · 1' Chain; 6' Wire



WG-Winter Gold



◀ **4786AS-000 CHANDELIER** · *Antique Silver*
27.75"W x 29"H · Canopy: 5"W x 1"H
6 – 60 Watt E12 Candelabra · Finish: AS
Includes Seeded Crystals · 10' Chain; 15' Wire

celine
collection
IN ANTIQUE SILVER

▶ **4781AS-000 SCONCE** · *Antique Silver*
5.50"W x 19.25"H x 9.50"E
Mirror Backplate: 5"W x 12"H x .75"E · Ctr/Top: 8.5"
Ctr/Btm: 10.75" · 1 – 60 Watt E12 Candelabra · Finish: AS
Includes Seeded Crystals · Damp Rated



Coordinates With

BLAIR
8553AS-299 VANITY
see page 75



BLAKELY
9484AS-CR PENDANT
see page 79



CORRIGAN
210941AS-652 PENDANT
see page 140



► **4782AS-000 CHANDELIER** · *Antique Silver*
49"W x 44.50"H · Canopy: 7"W x 1.50"H
12 – 60 Watt E12 Candelabra · Finish: AS
Includes Seeded Crystals · 10' Chain; 15' Wire



AS-Antique Silver



▲ **4780AS-000 CHANDELIER** • *Antique Silver*
57.50"W x 61.50"H • Canopy: 7" W x 1.5" H
16 – 60 Watt E12 Candelabra • Finish: AS
Includes Seeded Crystals • 10' Chain; 15' Wire

50+LBS

Additional mounting support required



◀ **4784AS-000 FOYER** · *Antique Silver*
21.75"W x 30.25"H · Canopy: 5"W x 1"H
4 – 60 Watt E12 Candelabra · Finish: AS
Includes Seeded Crystals · 10' Chain; 15' Wire

▶ **4788AS-000 CHANDELIER** · *Antique Silver*
33"W x 38.50"H · Canopy: 7"W x 1.50"H
10 – 60 Watt E12 Candelabra · Finish: AS
Includes Seeded Crystals · 10' Chain; 15' Wire



▶ **3074BB-292 CHANDELIER** · *Burnished Bronze*
24.50"W x 27.50"H · Canopy: 5"W x 1"H · 4 – 100 Watt
E26 Medium · Mist Scavo Glass · Finish: BB · 10' Chain;
15' Wire

▼ **3071BB CEILING** · *Burnished Bronze*
16"W x 16"H · Canopy: 6"W x 2"H
3 – 100 Watt E26 Medium · Mist Scavo Glass
Finish: BB



chandler

collection

IN BURNISHED BRONZE
& MATTE NICKEL



▶ **3071MN CEILING** · *Matte Nickel*
16"W x 16"H · Canopy: 6"W x 2"H · 3 – 100 Watt E26
Medium · White Faux Alabaster Glass · Finish: MN

◀ **3074MN-222 CHANDELIER** · *Matte Nickel*
24.50"W x 27.50"H · Canopy: 5"W x 1"H · 4 – 100 Watt
E26 Medium · White Faux Alabaster Glass · Finish: MN
10' Chain; 15' Wire

chandler | IN BURNISHED BRONZE & MATTE NICKEL



◀ **3075BB-292 CHANDELIER** · *Burnished Bronze*
26"W x 30.50"H · Canopy: 5"W x 1"H
5 – 100 Watt E26 Medium · Mist Scavo Glass
Finish: BB · 10' Chain; 15' Wire



▶ **3075MN-222 CHANDELIER** · *Matte Nickel*
26"W x 30.50"H · Canopy: 5"W x 1"H
5 – 100 Watt E26 Medium · White Faux Alabaster Glass
Finish: MN · 10' Chain; 15' Wire

chandler | IN BURNISHED BRONZE & MATTE NICKEL

▼ **3077BB ISLAND** · *Burnished Bronze*
 37"W x 23.50"H x 13"E · Canopy: 9"L x 5"W x 1"H
 2 – 100 Watt E26 Medium · Mist Scavo Glass
 Finish: BB · 10' Chain; 15' Wire



▲ **3070MN-222 MINI PENDANT** · *Matte Nickel*
 White Faux Alabaster Glass · Finish: MN

▲ **3070BB-292 MINI PENDANT** · *Burnished Bronze*
 Mist Scavo Glass · Finish: BB
 8"W x 44"H · 44"H Overall Includes 6", 12" &
 18"L Removable Rods · Canopy: 5.75"W x 2.25"H
 1 – 100 Watt E26 Medium · 1' Chain; 6' Wire



▲ **1781BB-292 SCONCE** · *Burnished Bronze*
 8"W x 10.25"H x 9.50"E · Backplate: 5.50"W x 7"H x 1"E
 Ctr/Top: 5.75" Ctr/Btm: 4.50" · 1 – 100 Watt E26
 Medium · Mist Scavo Glass · Finish: BB · Damp Rated



◀ **1781MN-222 SCONCE** · *Matte Nickel*
 8"W x 10.25"H x 9.50"E · Backplate: 5.50"W x 7"H x 1"E
 Ctr/Top: 5.75" Ctr/Btm: 4.50" · 1 – 100 Watt E26 Medium
 Faux White Alabaster Glass · Finish: MN · Damp Rated

chandler | IN BURNISHED BRONZE & MATTE NICKEL



◀ **1803MN-222 VANITY**

Matte Nickel


33"W x 10.25"H x 10"E
 Backplate: 7"W x 5.50"H x 1"E
 Ctr/Top: 6.25" Ctr/Btm: 4"
 3 – 100 Watt E26 Medium
 Faux White Alabaster Glass
 Finish: MN • Damp Rated



◀ **1803BB-292 VANITY**

Burnished Bronze

33"W x 10.25"H x 10"E
 Backplate: 7"W x 5.50"H x 1"E
 Ctr/Top: 6.25" Ctr/Btm: 4"
 3 – 100 Watt E26 Medium
 Mist Scavo Glass • Finish: BB
 Damp Rated



▲ **1804MN-222 VANITY** • *Matte Nickel*

43.50"W x 10.25"H x 10"E
 Backplate: 7"W x 5.50"H x 1"E • Ctr/Top: 6.25"
 Ctr/Btm: 4" • 4 – 100 Watt E26 Medium • White
 Faux Alabaster Glass • Finish: MN • Damp Rated



G222 GLASS

8"W x 5"H
 White Faux
 Alabaster



▲ **1804BB-292 VANITY** • *Burnished Bronze*

43.50"W x 10.25"H x 10"E
 Backplate: 7"W x 5.50"H x 1"E • Ctr/Top: 6.25"
 Ctr/Btm: 4" • 4 – 100 Watt E26 Medium
 Mist Scavo Glass • Finish: BB • Damp Rated



G292 GLASS

8"W x 5"H
 Mist Scavo

◀ **3944BB-201 CHANDELIER** • *Burnished Bronze*
19"W x 22"H • Canopy: 5"W x 1"H • 3 – 100 Watt E26
Medium • Tumbleweed Glass • Finish: BB
10' Chain; 15' Wire

▶ **3944BB-202 CHANDELIER** • *Burnished Bronze*
19"W x 22"H • Canopy: 5"W x 1"H • 3 – 100 Watt E26
Medium • Soft White Glass • Finishes: BB, MN
10' Chain; 15' Wire

chapman *collection*

IN BURNISHED BRONZE
& MATTE NICKEL

▲ **3944MN-202 CHANDELIER** • *Matte Nickel*
19"W x 22"H • Canopy: 5"W x 1"H • 3 – 100 Watt E26
Medium • Soft White Glass • Finishes: BB, MN
10' Chain; 15' Wire

▲ **8401BB-202 SCONCE** • *Burnished Bronze*
Soft White Glass • Finishes: BB, MN

▲ **8401BB-201 SCONCE** • *Burnished Bronze*
Tumbleweed Glass • Finish: BB

◀ **8401MN-202 SCONCE** • *Matte Nickel*
Soft White Glass • Finishes: BB, MN
6"W x 9"H x 7.50"E • Backplate:
4.5"W x 7"H x 1"E • Ctr/Top: 5.5" Ctr/Btm: 3.5"
1 – 100 Watt E26 Medium • Damp Rated

▶ **3949BB-202 CHANDELIER** • *Burnished Bronze*
28.50"W x 30.50"H • Canopy: 5"W x 1"H • 9 – 60 Watt
E26 Medium • Soft White Glass • Finishes: BB, MN
10' Chain; 15' Wire



▲ **3949BB-201 CHANDELIER** • *Burnished Bronze*
28.50"W x 30.50"H • Canopy: 5"W x 1"H • 9 – 60 Watt
E26 Medium • Tumbleweed Glass • Finish: BB
10' Chain; 15' Wire

▶ **3949MN-202 CHANDELIER** • *Matte Nickel*
28.50"W x 30.50"H • Canopy: 5"W x 1"H • 9 – 60 Watt
E26 Medium • Soft White Glass • Finishes: BB, MN
10' Chain; 15' Wire





◀ **3945BB-201 CHANDELIER** · *Burnished Bronze*
 24"W x 27.50"H · Canopy: 5"W x 1"H · 5 – 100 Watt
 E26 Medium · Tumbleweed Glass · Finish: BB
 10' Chain; 15' Wire

▶ **3945BB-202 CHANDELIER** · *Burnished Bronze*
 24"W x 27.50"H · Canopy: 5"W x 1"H · 5 – 100 Watt
 E26 Medium · Soft White Glass · Finishes: BB, MN
 10' Chain; 15' Wire



◀ **3945MN-202 CHANDELIER** · *Matte Nickel*
 24"W x 27.50"H · Canopy: 5"W x 1"H · 5 – 100 Watt
 E26 Medium · Soft White Glass · Finishes: BB, MN
 10' Chain; 15' Wire



▲ **3941MN-202 PENDANT** · *Matte Nickel*
 Soft White Glass · Finishes: BB, MN

▲ **3941BB-201 PENDANT** · *Burnished Bronze*
 Tumbleweed Glass · Finish: BB

▲ **3941BB-202 PENDANT** · *Burnished Bronze*
 Soft White Glass · Finishes: BB, MN
 5.75"W x 43"H · 43"H Overall Includes 6", 12" & 18"L
 Removable Rods · Canopy: 5.50"W x 1"H
 1 – 100 Watt E26 Medium · 1' Chain; 6' Wire



▲ **3947MN-SW SEMI-FLUSH** · *Matte Nickel*
Soft White Glass · Finishes: BB, MN

▶ **3947BB-SW SEMI-FLUSH** · *Burnished Bronze*
Soft White Glass · Finishes: BB, MN

▶ **3947BB-TW SEMI-FLUSH** · *Burnished Bronze*
Tumbleweed Glass · Finish: BB
17.50"W x 12"H · Canopy: 5.50"W x 1"H
3 – 100 Watt E26 Medium



◀ **3948BB-TW PENDANT** · *Burnished Bronze*
Tumbleweed Glass · Finish: BB

▼ **3948MN-SW PENDANT** · *Matte Nickel*
Soft White Glass · Finishes: BB, MN

▼ **3948BB-SW PENDANT** · *Burnished Bronze*
Soft White Glass · Finishes: BB, MN
17.50"W x 22"H · Canopy: 5.50"W x 1"H · 3 – 100 Watt E26
Medium · 10' Chain; 15' Wire





▲ **8402BB-201 VANITY** · *Burnished Bronze*
Tumbleweed Glass · Finish: BB

▶ **8402MN-202 VANITY** · *Matte Nickel*
Soft White Glass · Finishes: BB, MN

▶ **8402BB-202 VANITY** · *Burnished Bronze*
Soft White Glass · Finishes: BB, MN
16"W x 9"H x 7.50"E · Backplate: 8"W x 4.50"H x 1"E
Ctr/Top: 2.50" Ctr/Btm: 6.50 · 2 – 100 Watt E26
Medium · Damp Rated



◀ **8403MN-202 VANITY** · *Matte Nickel*
Soft White Glass · Finishes: BB, MN

◀ **8403BB-201 VANITY** · *Burnished Bronze*
Tumbleweed Glass · Finish: BB



▼ **8403BB-202 VANITY** · *Burnished Bronze*
Soft White Glass · Finishes: BB, MN

24"W x 9"H x 7.50"E
Backplate: 8"W x 4.50"H x 1"E
Ctr/Top: 6.50" Ctr/Btm: 2.50" · 3 – 100 Watt
E26 Medium · Damp Rated





▲ **8404MN-202 VANITY** · *Matte Nickel*

32"W x 9"H x 7.50"E · Backplate: 8"W x 4.50"H x 1"E
 Ctr/Top: 2.50" Ctr/Btm: 6.50" · 4 – 100 Watt E26 Medium
 Soft White Glass · Finishes: BB, MN · Damp Rated



▲ **8404BB-201 VANITY** · *Burnished Bronze*

32"W x 9"H x 7.50"E · Backplate: 8"W x 4.50"H x 1"E
 Ctr/Top: 2.50" Ctr/Btm: 6.50" · 4 – 100 Watt E26 Medium
 Tumbleweed Glass · Finish: BB · Damp Rated



▲ **8404BB-202 VANITY** · *Burnished Bronze*

32"W x 9"H x 7.50"E
 Backplate: 8"W x 4.50"H x 1"E · Ctr/Top: 2.50"
 Ctr/Btm: 6.50" · 4 – 100 Watt E26 Medium
 Soft White Glass · Finishes: BB, MN · Damp Rated



G201 GLASS
6"W x 5"H



G202 GLASS
6"W x 5"H



charleston

collection

IN SILVER AND GOLD LEAF



charleston | IN SILVER AND GOLD LEAF



◀ **413301SG CHANDELIER** · *Silver and Gold Leaf*
 33.50"W x 35"H · Canopy: 5"W x 1"H · 10 – 60 Watt E12
 Candelabra · Finish: SG · Includes Crystal Adornments
 10' Chain; 15' Wire



▲ **313341SG PENDANT** · *Silver and Gold Leaf*
 23"W x 29.50"H · Canopy: 5"W x 1"H · 4 – 60 Watt E12
 Candelabra · Finish: SG · Includes Crystal Adornment
 10' Chain; 15' Wire



◀ **313342SG PENDANT**
Silver and Gold Leaf
 15"W x 26.50"H
 Canopy: 5"W x 1"H · 4 – 60 Watt
 E12 Candelabra · Finish: SG
 Includes Crystals · 10' Chain; 15' Wire



SH654 SHADE
 6"W x 4.75"H
 Stay-Straight Shade

▲ **613311SG-654 SCONCE** · *Silver and Gold Leaf*
 6"W x 17.50"H x 11.50"E · Mirror Backplate:
 5"W x 15"H x .75"E · Ctr/Top: 10" Ctr/Btm: 7.50" · 1 – 60
 Watt E12 Candelabra · Decorative White Fabric Stay-Straight
 Shade Finish: SG · Includes Crystal Adornment · Damp Rated



▲ **413361SG CHANDELIER** · *Silver and Gold Leaf*
 26"W x 32"H · Canopy: 5"W x 1"H · 6 – 60 Watt E12
 Candelabra · Finish: SG · Includes Crystal Adornments
 10' Chain; 15' Wire



chastain
collection

IN TOBACCO



Coordinates
With

213911BB-LD CEILING
see page 416



PERRY
4864BA PENDANT
see page 263



S546 SHADE
5.5"W x 4.25"H
Stay-Straight
Shade

▲ **4209TB-546 CHANDELIER** • *Tobacco*
32.50"W x 30.25"H • Canopy: 5.50"W x 1"H
9 – 60 Watt E12 Candelabra • Decorative White Fabric
Stay-Straight Shades • Finish: TB • 10' Chain; 15' Wire

▶ **4206TB-546 CHANDELIER** · *Tobacco*
29.25"W x 24.50"H · Canopy: 5.50"W x 1"H · 6 – 60 Watt
E12 Candelabra · Decorative White Fabric Stay-Straight
Shades · Finish: TB · 10' Chain; 15' Wire



◀ **1717TB-546 SCONCE** · *Tobacco*
11.50"W x 12.50"H x 6"E · Backplate: 5"W x 5"H x .75"E
Ctr/Top: 9.50" Ctr/Btm: 3.50" · 2 – 60 Watt E12
Candelabra · Decorative White Fabric Stay-Straight
Shades · Finish: TB · Damp Rated



▶ **1716TB-546 SCONCE** · *Tobacco*
5.25"W x 18.50"H x 6.25"E · Backplate: 5"W x 5"H x .75"E
Ctr/Top: 10" Ctr/Btm: 8.5" · 1 – 60 Watt E12 Candelabra
Decorative White Fabric Stay-Straight Shade · Finish: TB
Damp Rated



◀ **4208TB FOYER** · *Tobacco*

20.25"W x 20"H · Canopy: 5.50"W x 1"H
4 – 60 Watt E12 Candelabra · Finish: TB
10' Chain; 15' Wire

4208TB FOYER

Includes Flush
Mount Option
20.25"W x 19"H



▶ **4204TB CHANDELIER** · *Tobacco*

14"W x 13"H · Canopy: 5.50"W x 1"H · 4 – 60 Watt E12
Candelabra · Finish: TB · 4' Chain; 6' Wire





chateau
collection

IN FRENCH OAK



◀ **4098FO CHANDELIER** · *French Oak*

53.50"W x 63"H · Canopy: 7"W x 1.50"H

16 – 60 Watt E12 Candelabra · Finish: FO

Includes Decorative Fobs · 10' Chain; 15' Wire

50+LBS

Additional mounting support required

▶ **4096FO CHANDELIER** · *French Oak*

28"W x 31.75"H · Canopy: 5"W x 1.25"H

6 – 60 Watt E12 Candelabra · Finish: FO

Includes Decorative Fobs · 10' Chain; 15' Wire



FO-French Oak



◀ **4090FO CHANDELIER** • *French Oak*
35"W x 38.25"H • Canopy: 6"W x 1.25"H
10 – 60 Watt E12 Candelabra • Finish: FO
Includes Decorative Fobs • 10' Chain; 15' Wire

▶ **1607FO SCONCE** • *French Oak*
7.75"W x 19"H x 5.50"E
Backplate: 5.25"W x 7"H x 1"E • Ctr/Top: 11" Ctr/Btm:
8" • 2 – 60 Watt E12 Candelabra • Finish: FO
Includes Decorative Fobs • Damp Rated

▶ **1606FO SCONCE** • *French Oak*
5.25"W x 16.25"H x 6.25"E
Backplate: 5.25"W x 7"H x 1"E • Ctr/Top: 11" Ctr/Btm:
5.25" • 1 – 60 Watt E12 Candelabra • Finish: FO
Includes Decorative Fobs • Damp Rated



▼ **4094FO PETITE** · *French Oak* · 15.50"W x 23"H
 Canopy: 5"W x 1.25"H · 4 – 60 Watt E12 Candelabra
 Finish: FO · Includes Decorative Fobs · 10' Chain;
 15' Wire



**4094FO
 CHANDELIER**
 Includes Flush
 Mount Option
 15.50"W x 21.25"H



▲ **9471FO FOYER** · *French Oak*
 12.50"W x 21"H · Canopy: 5.25"W x 1.50"H
 3 – 60 Watt E12 Candelabra · Finish: FO
 Includes Decorative Fobs · 10' Chain; 15' Wire



◀ **9472FO FOYER** · *French Oak*
 17"W x 29.50"H · Canopy: 5.25"W x 1.50"H
 3 – 60 Watt E12 Candelabra · Finish: FO
 Includes Decorative Fob · 10' Chain; 15' Wire

▶ **9473FO FOYER** · *French Oak*
 25"W x 38"H · Canopy: 5.25"W x 1.50"H
 4 – 60 Watt E12 Candelabra · Finish: FO
 Includes Decorative Fob · 10' Chain; 15' Wire






city
collection

IN POLISHED NICKEL

► **319201PN PENDANT** · *Polished Nickel*
29"W x 63"H · 63"H Overall Includes 6", 12" & 18"L
Removable Rods · Canopy: 5" W x .75"H · 12 – 60 Watt
E12 Candelabra · Finish: PN · 1' Chain; 6' Wire



◄ **419201PN CHANDELIER** · *Polished Nickel*
23.50"W x 60.50"H · 60.50"H Overall Includes 6", 12"
& 18"L Removable Rods · Canopy: 5"W x .75"H · 16 – 60
Watt E12 Candelabra · Finish: PN · 1' Chain; 6' Wire





▲ **219281PN CEILING** · *Polished Nickel*
19"W x 7.25"H · Canopy: 5"W x .75"H · 8 – 60 Watt
E12 Candelabra · Finish: PN · Damp Rated



▶ **619281PN SCONCE** · *Polished Nickel*
11.50"W x 19"H x 4"E · Backplate: 5"W x 8"H x .75"E
Ctr/Top: 9.5" Ctr/Btm: 9.5" · 8 – 60 Watt E12 Candelabra
Finish: PN · Damp Rated



▲ **519241PN FOYER** • *Polished Nickel*
 16.50"W x 29.25"H • Canopy: 5"W x .75"H • 4 – 60 Watt
 E12 Candelabra • Finish: PN • 10' Chain; 15' Wire

Coordinates With

ZANDER
621931PN SCONCE
 see page 344



MID-CENTURY
321142PN PENDANT
 see page 224



► **419281PN CHANDELIER** • *Polished Nickel*
 29"W x 63.75"H • 63.75"H Overall Includes 6", 12" & 18"L
 Removable Rods • Canopy: 5"W x .75"H • 8 – 60 Watt E12
 Candelabra • Finish: PN • 1' Chain; 6' Wire



cole

collection

IN AGED BRASS & OLD BRONZE



◀ **421301AO CHANDELIER** · *Aged Brass & Old Bronze*
35.75"W x 39.50"H · Canopy: 5"W x 1"H · 10 – 60 Watt
E12 Candelabra · Finish: AO · 10' Chain; 15' Wire


▶ **421361AO CHANDELIER** · *Aged Brass & Old Bronze*
28.25"W x 29.50"H · Canopy: 5"W x 1"H · 6 – 60 Watt E12
Candelabra · Finish: AO · 10' Chain; 15' Wire



AO-Aged Brass & Old Bronze

► **521342AO FOYER** · *Aged Brass & Old Bronze*
15"W x 27.25"H · Canopy: 5"W x 1"H · 4 – 60 Watt E12
Candelabra · Finish: AO · 10' Chain; 15' Wire

▼ **521381AO FOYER** · *Aged Brass & Old Bronze*
22"W x 38"H · Canopy: 5"W x 1"H · 8 – 60 Watt E12
Candelabra · Finish: AO · 10' Chain; 15' Wire



► **521343AO FOYER** · *Aged Brass & Old Bronze*
16"W x 29"H · Canopy: 5"W x 1"H · 4 – 60 Watt E12
Candelabra · Finish: AO · 10' Chain; 15' Wire



◀ **521341AO FOYER** · *Aged Brass & Old Bronze*
 12"W x 16"H · Canopy: 5"W x 1"H · 4 – 60 Watt E12
 Candelabra · Finish: AO · 10' Chain; 15' Wire


▼ **121321AO-427 VANITY** · *Aged Brass & Old Bronze*
 14.50"W x 11.75"H x 6.25"E · Backplate: 13.50"W x 5"H x .75"E
 Ctr/Top: 8.25" Ctr/Btm: 3.50" · 2 – 100 Watt E26 Medium
 Clear Water Glass · Finish: AO · Damp Rated



▲ **621311AO SCONCE** · *Aged Brass & Old Bronze*
 5.25"W x 18"H x 7"E · Backplate: 5.25"W x 18"H x .75"E
 Ctr/Top: 9" Ctr/Btm: 9" · 1 – 60 Watt E12 Candelabra
 Finish: AO · Damp Rated



▼ **121331AO-427 VANITY** · *Aged Brass & Old Bronze*
 24"W x 11.75"H x 6.25"E · Backplate: 22.75"W x 5"H x .75"E
 Ctr/Top: 8.25" Ctr/Btm: 3.50" · 3 – 100 Watt E26 Medium
 Clear Water Glass · Finish: AO · Damp Rated



GL427 GLASS
 5.25"W x 5.5"H x
 5.25"E



▼ **121341AO-427 VANITY** · *Aged Brass & Old Bronze*
 33"W x 11.75"H x 6.25"E · Backplate: 32"W x 5"H x .75"E
 Ctr/Top: 8.25" Ctr/Btm: 3.50" · 4 – 100 Watt E26 Medium
 Clear Water Glass · Finish: AO · Damp Rated





corrigan
collection

IN ANTIQUE SILVER



◀ **410961AS-315 CHANDELIER** · *Antique Silver*
28.50"W x 27"H · Canopy: 5"W x 1"H · 6 – 100 Watt
E26 Medium · Silver Mercury Glass · Finish: AS
10' Chain; 15' Wire

▶ **410901AS-315 CHANDELIER** · *Antique Silver*
38"W x 42.25"H · Canopy: 5"W x 1"H · 10 – 60 Watt
E26 Medium · Silver Mercury Glass · Finish: AS
10' Chain; 15' Wire





◀ **210941AS-652 PENDANT** · *Antique Silver*
 15"W x 16.50"H · Canopy: 5"W x .75"H · 4 – 60 Watt
 E12 Candelabra · Decorative White Fabric Shade
 Frosted Glass Diffuser with K9 Crystal Finial
 Finish: AS · 10' Chain; 15' Wire

**210941AS-652
 CEILING**
 Includes Flush
 Mount Option
 15"W x 15"H



 **GL315 GLASS**
 6.25"W x 5"H



▲ **110921AS-315 VANITY** · *Antique Silver*
 14"W x 8"H x 7.25"E · Backplate: 7"W x 5.25"H x 1"E
 Ctr/Top: 2.50" Ctr/Btm: 5.50" · 2 – 100 Watt E26
 Medium · Silver Mercury Glass · Finish: AS
 Damp Rated



▲ **110931AS-315 VANITY** · *Antique Silver*
 22.50"W x 8"H x 7.25"E · Backplate: 7"W x 5.25"H x 1"E
 Ctr/Top: 2.50" Ctr/Btm: 5.50" · 3 – 100 Watt E26
 Medium · Silver Mercury Glass · Finish: AS · Damp Rated



◀ **810981AS-650 ISLAND** • *Antique Silver*
32" W x 68.25" H x 23" E • 68"H Overall Includes
6", 12" & 18"L Removable Rods • Canopy: 8"L x 5.50"W
x .75"H • 8 – 60 Watt E12 Candelabra
Decorative White Fabric Shade • Finish: AS • K9 Crystal •
1' Chain; 6' Wire

▶ **610911AS-315 SCONCE** • *Antique Silver*
6.25"W x 16"H x 6.75"E • Backplate: 5"W x 5"H x 1"E
Ctr/Top: 6" Ctr/Btm: 10" • 1 – 100 Watt E26 Medium
Silver Mercury Glass • Finish: AS • Damp Rated



◀ **310961AS-651 PENDANT** • *Antique Silver*
24"W x 22.50"H • Canopy: 5"W x 1"H • 6 – 60 Watt E12
Candelabra • Decorative White Fabric Shade • Finish: AS •
K9 Crystal • 10' Chain; 15' Wire

- ▶ **6301BB-489 SCONCE** · *Burnished Bronze*
- ▶ **6301AN-489 SCONCE** · *Antique Nickel*

5"W x 15.50"H x 5.25"E
 Backplate: 5"W x 8"H x 0.75"E · Ctr/Top: 11"
 Ctr/Btm: 4.50" · 1 – 60 Watt E12 Candelabra
 Decorative White Fabric Clip-On Shade · Finishes:
 AN, BB · Damp Rated



covington

collection

IN ANTIQUE NICKEL
 & BURNISHED BRONZE

9401BB FOYER

Includes Chain
 Mount Option
 16"W x 25.5"H



▲ **9401BB FOYER** · *Burnished Bronze*
 16"W x 26"H · Canopy: 5"W x 1"H
 3 – 60 Watt E12 Candelabra · Clear Hand-Blown
 Glass · Finishes: AN, BB · 10' Chain; 15' Wire

▶ **9401AN FOYER** · *Antique Nickel*
 16"W x 26"H · Canopy: 5"W x 1"H
 3 – 60 Watt E12 Candelabra · Clear Hand-Blown
 Glass · Finishes: AN, BB · 10' Chain; 15' Wire

9401AN FOYER

Includes Chain
 Mount Option
 16"W x 25.5"H





◀ **4046BB-489 CHANDELIER** · *Burnished Bronze*
29"W x 29"H · Canopy: 5"W x 1"H · 6 – 60 Watt E12
Candelabra · Decorative White Fabric Clip-On Shades
Finishes: AN, BB · 10' Chain; 15' Wire

▶ **4046AN-489 CHANDELIER** · *Antique Nickel*
29"W x 29"H · Canopy: 5"W x 1"H · 6 – 60 Watt E12
Candelabra · Decorative White Fabric Clip-On Shades
Finishes: AN, BB · 10' Chain; 15' Wire



**S489 FABRIC
SHADE**
4.5"W x 6"H





▲ **9411BB FOYER** · *Burnished Bronze*
 11"W x 13.50"H · Canopy: 5"W x 1"H
 3 – 60 Watt E12 Candelabra · Clear
 Hand-Blown Glass · Finishes: AN, BB
 10' Chain; 15' Wire

9411AN FOYER

Includes Flush
 Mount Option
 11"W x 12"H



▼ **9411AN FOYER** · *Antique Nickel*
 11"W x 13.50"H · Canopy: 5"W x 1"H
 3 – 60 Watt E12 Candelabra · Clear Hand-Blown Glass
 Finishes: AN, BB · 10' Chain; 15' Wire



9411BB FOYER

Includes Flush
 Mount Option
 11"W x 12"H



▲ **2323AN-SW CEILING** · *Antique Nickel*
 12.50"W x 4.50"H · Canopy: 12.50"W x 1"H
 2 – 60 Watt E26 Medium

2325AN-SW CEILING · *Antique Nickel*
 14.75"W x 5.25"H · Canopy: 14.75"W x 1"H
 3 – 60 Watt E26 Medium

Soft White Glass · Finishes: AD, AN, BB, CG,
 PN, SA, WG · Damp Rated



▲ **2323BB-SW CEILING** · *Burnished Bronze*
 12.50"W x 4.50"H · Canopy: 12.50"W x 1"H
 2 – 60 Watt E26 Medium

2325BB-SW CEILING · *Burnished Bronze*
 14.75"W x 5.25"H · Canopy: 14.75"W x 1"H
 3 – 60 Watt E26 Medium

Soft White Glass · Finishes: AD, AN, BB, CG,
 PN, SA, WG · Damp Rated



▲ **8442AN-102 VANITY** • *Antique Nickel*
 12.50"W x 9"H x 6.25"E • Backplate: 8"W x 5"H x 1"E
 Ctr/Top: 5" Ctr/Btm: 4" • 2 – 75 Watt E26 Medium
 Soft White Glass • Finishes: AN, BB • Damp Rated



G102 GLASS
 4.25"W x 6.25"H
 Soft White



▲ **8442BB-102 VANITY** • *Burnished Bronze*
 12.50"W x 9"H x 6.25"E • Backplate: 8"W x 5"H x 1"E
 Ctr/Top: 4" Ctr/Btm: 5" • 2 – 75 Watt E26 Medium
 Soft White Glass • Finishes: AN, BB • Damp Rated

▶ **8443AN-102 VANITY** • *Antique Nickel*
 19.25"W x 9"H x 6.25"E
 Backplate: 8"W x 5"H x 1"E • Ctr/Top: 4"
 Ctr/Btm: 5" • 3 – 75 Watt E26 Medium • Soft
 White Glass • Finishes: AN, BB • Damp Rated



◀ **8443BB-102 VANITY** • *Burnished Bronze*
 19.25"W x 9"H x 6.25"E • Backplate: 8"W x 5"H x 1"E
 Ctr/Top: 5" Ctr/Btm: 4" • 3 – 75 Watt E26 Medium
 Soft White Glass • Finishes: AN, BB • Damp Rated



dawson
collection

IN AGED BRASS

▶ **419391AD CHANDELIER** • *Aged Brass*
30"W x 38.25"H • Canopy: 5"W x 1"H • 10 – 60 Watt
E12 Candelabra • Finish: AD • 10' Chain; 15' Wire



◀ **419361AD CHANDELIER** • *Aged Brass*
24.75"W x 29.50"H • Canopy: 5"W x 1"H • 6 – 60 Watt
E12 Candelabra • Finish: AD • 10' Chain; 15' Wire



AD-Aged Brass



◀ **519341AD FOYER** · *Aged Brass*
 14"W x 19"H · Canopy: 5"W x 1"H · 4 – 60 Watt
 E12 Candelabra · Finish: AD · 10' Chain; 15' Wire

▶ **519342AD FOYER** · *Aged Brass*
 18"W x 26.50"H · Canopy: 5"W x 1"H · 4 – 60 Watt
 E12 Candelabra · Finish: AD · 10' Chain; 15' Wire



◀ **619311AD-674 SCONCE** · *Aged Brass*
 6"W x 17"H x 8"E · Backplate: 5"W x 5"H x .75"E
 Ctr/Top: 14.25" Ctr/Btm: 2.75" · 1 – 60 Watt E12 Candelabra
 Decorative White Fabric Stay-Straight Shade · Finish: AD
 Damp Rated





▲ **119341AD-674 VANITY** · *Aged Brass*
 35.25"W x 12"H x 7.25"E · Backplate: 5"W x 5"H x .75"E
 Ctr/Top: 9.50" Ctr/Btm: 2.50" · 4 – 60 Watt E12 Candelabra
 Decorative White Fabric Stay-Straight Shades · Finish: AD
 Damp Rated



▲ **119331AD-674 VANITY** · *Aged Brass*
 25.50"W x 12"H x 7.25"E · Backplate: 5"W x 5"H x .75"E
 Ctr/Top: 9.50" Ctr/Btm: 2.50" · 3 – 60 Watt E12 Candelabra
 Decorative White Fabric Stay-Straight Shades · Finish: AD
 Damp Rated



◀ **119321AD-674 VANITY** · *Aged Brass*
 16"W x 12"H x 7.25"E · Backplate: 5"W x 5"H x .75"E
 Ctr/Top: 9.50" Ctr/Btm: 2.50" · 2 – 60 Watt E12 Candelabra
 Decorative White Fabric Stay-Straight Shades · Finish: AD
 Damp Rated



eastman
collection

IN SILVER AND BRONZE



◀ **4884SZ PENDANT** • *Silver and Bronze*
 18"W x 14.50"H • Canopy: 5"W x 1"H • 4 – 100 Watt E26
 Medium • Finish: SZ • 10' Chain; 15' Wire

▼ **4886SZ PENDANT** • *Silver and Bronze*
 24.75"W x 14.25"H • Canopy: 5"W x 1"H • 6 – 100 Watt
 E26 Medium • Finish: SZ • 10' Chain; 15' Wire



▲ **4883SZ PENDANT** • *Silver and Bronze*
 15"W x 13.75"H • Canopy: 5"W x 1"H • 3 – 100 Watt
 E26 Medium • Finish: SZ • 10' Chain; 15' Wire



▲ **4881SZ SCONCE** • *Silver and Bronze*
 5"W x 12"H x 4"E • Backplate: 5"W x 12"H x .75"E
 Ctr/Top: 6" Ctr/Btm: 6" • 1 – 60 Watt E26 Medium
 Finish: SZ • Damp Rated • **ADA**



SZ-Silver and Bronze



ellis

collection

IN ANTIQUE SILVER,
BRUSHED GOLD &
CAPITAL GOLD





◀ **4542CG PENDANT** • *Capital Gold*
26"W x 28.25"H • Canopy: 5"W x 1"H
4 – 60 Watt E12 Candelabra • Finishes: AS,
BG, CG • 10' Chain; 15' Wire



▲ **4542AS PENDANT** • *Antique Silver*
26"W x 28.25"H • Canopy: 5"W x 1"H
4 – 60 Watt E12 Candelabra • Finishes: AS,
BG, CG • 10' Chain; 15' Wire



◀ **4542BG PENDANT** • *Brushed Gold*
26"W x 28.25"H • Canopy: 5"W x 1"H
4 – 60 Watt E12 Candelabra • Finishes: AS,
BG, CG • 10' Chain; 15' Wire



◀ **4541CG PENDANT** · *Capital Gold*
 18"W x 20.25"H · Canopy: 5"W x 1"H · 4 – 60 Watt E12
 Candelabra · Finishes: AS, BG, CG · 10' Chain; 15' Wire



▲ **4541AS PENDANT** · *Antique Silver*
 ▲ **4541BG PENDANT** · *Brushed Gold*



18"W x 20.25"H · Canopy: 5"W x 1"H · 4 – 60 Watt E12
 Candelabra · Finishes: AS, BG, CG · 10' Chain; 15' Wire



▲ **4546CG-566 SCONCE** · *Capital Gold*
 ▶ **4546AS-566 SCONCE** · *Antique Silver*
 ▶ **4546BG-566 SCONCE** · *Brushed Gold*

10"W x 12"H x 5"E · Backplate: 6.25"W x 8"H x .75"E
 Ctr/Top: 6" Ctr/Btm: 6" · 2 – 40 Watt E12 Candelabra
 Decorative White Fabric Shade · Finishes: AS, BG, CG





◀ **4545CG-582 PENDANT** · *Capital Gold*
 18.25"W x 14"H · Canopy: 5"W x 1"H · 3 – 60 Watt
 E26 Medium · Decorative White Fabric Shade
 Frosted Glass Diffuser with Finial · Finishes:
 AS, BG, CG · 10' Chain; 15' Wire

**4545CG-582
 PENDANT**
 Includes
 Semi-Flush
 Mount Option
 18.25"W x 15.5"H



**4545AS-582
 PENDANT**
 Includes
 Semi-Flush
 Mount Option
 18.25"W x 15.5"H



▶ **4545AS-582 PENDANT** · *Antique Silver*
 18.25"W x 14"H · Canopy: 5"W x 1"H · 3 – 60 Watt
 E26 Medium · Decorative White Fabric Shade
 Frosted Glass Diffuser with Finial · Finishes:
 AS, BG, CG · 10' Chain; 15' Wire



◀ **4545BG-582 PENDANT** · *Brushed Gold*
 18.25"W x 14"H · Canopy: 5"W x 1"H · 3 – 60 Watt
 E26 Medium · Decorative White Fabric Shade
 Frosted Glass Diffuser with Finial · Finishes:
 AS, BG, CG · 10' Chain; 15' Wire

**4545BG-582
 PENDANT**
 Includes
 Semi-Flush
 Mount Option
 18.25"W x 15.5"H





◀ **4543CG-578 PENDANT** · *Capital Gold*
22"W x 21"H · Canopy: 5"W x 1"H · 5 – 60 Watt E26
Medium · Decorative White Fabric Shade · Frosted Glass
Diffuser with Finial · Finishes: AS, BG, CG · 10' Chain;
15' Wire

▶ **4543AS-578 PENDANT** · *Antique Silver*
22"W x 21"H · Canopy: 5"W x 1"H · 5 – 60 Watt
E26 Medium · Decorative White Fabric Shade
Frosted Glass Diffuser with Finial · Finishes:
AS, BG, CG · 10' Chain; 15' Wire



◀ **4543BG-578 PENDANT** · *Brushed Gold*
22"W x 21"H · Canopy: 5"W x 1"H · 5 – 60 Watt E26
Medium · Decorative White Fabric Shade · Frosted Glass
Diffuser with Finial · Finishes: AS, BG, CG · 10' Chain;
15' Wire



▲ **4544AS-579 PENDANT** · *Antique Silver*
 10"W x 13.50"H · Canopy: 5"W x 1"H · 2 – 60 Watt
 E12 Candelabra · Decorative White Fabric Shade
 Frosted Glass Diffuser with Finial · Finishes:
 AS, BG, CG · 10' Chain; 15' Wire



▲ **4544CG-579 PENDANT** · *Capital Gold*
 ▲ **4544BG-579 PENDANT** · *Brushed Gold*
 10"W x 13.50"H · Canopy: 5"W x 1"H · 2 – 60 Watt
 E12 Candelabra · Decorative White Fabric Shade
 Frosted Glass Diffuser with Finial · Finishes:
 AS, BG, CG · 10' Chain; 15' Wire



▲ **4549AS CEILING** · *Antique Silver*
 16"W x 8.50"H · 3 – 60 Watt E26 Medium
 Decorative White Fabric Shade ·
 Frosted Glass Diffuser with Finial · Finishes:
 AS, BG, CG



▲ **4549BG CEILING** · *Brushed Gold*
 16"W x 8.50"H · 3 – 60 Watt E26 Medium
 Decorative White Fabric Shade ·
 Frosted Glass Diffuser with Finial · Finishes:
 AS, BG, CG



◀ **4549CG CEILING** · *Capital Gold*
 16"W x 8.50"H · 3 – 60 Watt E26 Medium
 Decorative White Fabric Shade ·
 Frosted Glass Diffuser with Finial · Finishes:
 AS, BG, CG

▶ **4736BN-150 CHANDELIER** • *Brushed Nickel*
23"W x 21.50"H • Canopy: 5"W x 1"H • 6 – 60 Watt
E12 Candelabra • Clear Fluted Glass • Finish: BN
10' Chain; 15' Wire



emery
collection

IN BRUSHED NICKEL



◀ **4734BN-150 CHANDELIER** • *Brushed Nickel*
15.75"W x 17"H • Canopy: 5"W x 1"H • 4 – 60 Watt
E12 Candelabra • Clear Fluted Glass • Finish: BN
10' Chain; 15' Wire



◀ **8041BN-150 SCONCE** • *Brushed Nickel*
 4.50"W x 9"H x 4"E • Backplate: 4.50"W x 6"H x .75"E
 Ctr/Top: 5.75" Ctr/Btm: 3.25" • 1 – 60 Watt E12
 Candelabra • Clear Fluted Glass • Finish: BN
 Damp Rated • **ADA**



▶ **8042BN-150 VANITY** • *Brushed Nickel*
 8.50"W x 9.75"H x 4"E
 Backplate: 6"W x 4.5"H x .75"E • Ctr/Top: 7.50"
 Ctr/Btm: 2.25" • 2 – 60 Watt E12 Candelabra • Clear
 Fluted Glass • Finish: BN • Damp Rated • **ADA**



◀ **8043BN-150 VANITY** • *Brushed Nickel*
 14.50"W x 9.75"H x 4"E
 Backplate: 6"W x 4.50"H x .75"E • Ctr/Top: 7.50"
 Ctr/Btm: 2.25" • 3 – 60 Watt E12 Candelabra • Clear
 Fluted Glass • Finish: BN • Damp Rated • **ADA**

▶ **8044BN-150 VANITY** • *Brushed Nickel*
 21.75"W x 9.75"H x 4"E
 Backplate: 6"W x 4.50"H x .75"E • Ctr/Top: 7.50"
 Ctr/Btm: 2.25" • 4 – 60 Watt E12 Candelabra • Clear
 Fluted Glass • Finish: BN • Damp Rated • **ADA**





everleigh
collection

IN FRENCH GREIGE



◀ **417761FG CHANDELIER** • *French Greige*
30"W x 28.25"H • Canopy: 5"W x 1"H
6 – 60 Watt E12 Candelabra • Finish: FG
K9 Crystal Column • 10' Chain; 15' Wire

▶ **417701FG CHANDELIER** • *French Greige*
49.50"W x 46"H • Canopy: 7"W x 1.50"H
16 – 60 Watt E12 Candelabra • Finish: FG
K9 Crystal Column • 10' Chain; 15' Wire

50+LBS


Additional mounting support required



FG-French Greige



▲ **617711FG-660 SCONCE** · *French Greige*
 6.75"W x 21"H x 9.50"E
 Backplate: 5"W x 9"H x 1"E · Ctr/Top: 14.25"
 Ctr/Btm: 6.75" · 1 – 60 Watt E12 Candelabra
 Decorative White Fabric Stay-Straight Shade
 Finish: FG · K9 Crystal Column · Damp Rated



SH660 SHADE
 6.75"W x 4.5"H
 Stay-Straight Shade



◀ **117721FG-303 VANITY**
French Greige
 17.25"W x 11.50"H x 7"E
 Backplate: 8.50"W x 5"H x .75"E
 Ctr/Top: 2.50" Ctr/Btm: 9"
 2 – 100 Watt E26 Medium
 Soft White Glass
 Finish: FG · Damp Rated

▼ **117731FG-303 VANITY** · *French Greige*
 25.50"W x 11.50"H x 7"E · Backplate: 8.50"W x 5"H x .75"E
 Ctr/Top: 2.50" Ctr/Btm: 9" · 3 – 100 Watt E26 Medium
 Soft White Glass · Finish: FG · Damp Rated



▲ **117741FG-303 VANITY** · *French Greige*
 38.50"W x 11.50"H x 7"E
 Backplate: 8.50"W x 5"H x .75"E · Ctr/Top: 2.50"
 Ctr/Btm: 9" · 4 – 100 Watt E26 Medium
 Soft White Glass · Finish: FG · Damp Rated



GL303 GLASS
 5.25"W x 5.5"H



◀ **517761FG FOYER** · *French Greige*
24"W x 41.25"H · Canopy: 5"W x 1"H
6 – 60 Watt E12 Candelabra · Finish: FG
K9 Crystal Column · 10' Chain; 15' Wire



▶ **517741FG FOYER** · *French Greige*
16"W x 28.50"H · Canopy: 5"W x 1"H
4 – 60 Watt E12 Candelabra · Finish: FG
K9 Crystal Column · 10' Chain; 15' Wire

▶ **417702FG CHANDELIER** · *French Greige*
35"W x 33"H · Canopy: 5"W x 1"H
12 – 60 Watt E12 Candelabra · Finish: FG
K9 Crystal Column · 10' Chain; 15' Wire




◀ **9083WG-484 FOYER** · *Winter Gold*
26.25"W x 47"H · Canopy: 5.50"W x 1.50"H
6 – 60 Watt E12 Candelabra · Decorative
White Fabric Box-Pleated Stay-Straight
Shades · Finish: WG · 10' Chain; 15' Wire

▶ **9081WG-485 FOYER** · *Winter Gold*
8.50"W x 18.50"H · Canopy: 5.50"W x 1.50"H
1 – 60 Watt E26 Medium · Decorative White
Fabric Box-Pleated Shade · Frosted Glass Diffuser
with Finial · Finish: WG · 10' Chain; 15' Wire



fifth avenue *collection*

IN WINTER GOLD



◀ **4001WG-485 PENDANT** · *Winter Gold*
7"W x 53.50"H · 53.50"H Overall Includes 6", 12"
& 18"L Removable Rods · Canopy: 6"W x 1"H
1 – 60 Watt E26 Medium · Decorative White Fabric
Box-Pleated Shade · Frosted Glass
Diffuser with Finial · Finish: WG · 1' Chain; 6' Wire

▶ **9082WG-484 FOYER** · *Winter Gold*
19.50"W x 33.50"H · Canopy: 5.50"W x 1.50"H
3 – 60 Watt E12 Candelabra · Decorative White
Fabric Box-Pleated Stay-Straight Shades · Finish:
WG · 10' Chain; 15' Wire

▼ **4006WG-484 CHANDELIER** • *Winter Gold*
 28"W x 20"H • Canopy: 5.50"W x 1.50"H • 6 – 60 Watt
 E12 Candelabra • Decorative White Fabric Box-Pleated
 Stay-Straight Shades • Finish: WG • 10' Chain; 15' Wire



▼ **4007WG-500 PETITE** • *Winter Gold*
 18"W x 22"H • Canopy: 5"W x 1.50"H • 3 – 60
 Watt E12 Candelabra • Decorative White Fabric
 Box-Pleated Stay-Straight Shades • Finish: WG
 10' Chain; 15' Wire



◀ **4009WG-484 CHANDELIER** • *Winter Gold*
 32"W x 26"H • Canopy: 5.50"W x 1.50"H
 9 – 60 Watt E12 Candelabra • Decorative
 White Fabric Box-Pleated Stay-Straight
 Shades • Finish: WG • 10' Chain; 15' Wire

▶ **9172WG FOYER** · *Winter Gold*
 10"W x 20.50"H · Canopy: 5"W x 1.75"H · 2 – 60 Watt E12
 Candelabra · Painted Crystals · Finish: WG · 10' Chain; 15' Wire



▲ **4005WG-486 PENDANT** · *Winter Gold*
 22"W x 58.50"H · 58.50"H Overall Includes 6", 12"
 & 18"L Removable Rods · Canopy: 5.50"W x 1.50"H
 3 – 60 Watt E26 Medium · Decorative White Fabric
 Box-Pleated Shade · Frosted Glass Diffuser with Finial
 Finish: WG · 1' Chain; 6' Wire



▲ **9173WG CEILING** · *Winter Gold*
 14"W x 9.50"H · Canopy: 5"W x 1.75"H
 3 – 60 Watt E12 Candelabra · Painted Crystals
 Finish: WG

▲ **4003WG-487 CEILING** · *Winter Gold*
 15"W x 12"H · Canopy: 6"W x 1"H · 3 – 60 Watt
 E26 Medium · Decorative White Fabric Box-Pleated
 Shade · Frosted Glass Diffuser with Finial · Finish:
 WG · Damp Rated




◀ **1987WG-484 SCONCE** · *Winter Gold*

14.5"W x 14"H x 8"E · Backplate: 6"W x 6"H x 1.50"E
 Ctr/Top: 11.50" Ctr/Btm: 2.50" · 2 – 60 Watt E12 Candelabra
 Decorative White Fabric Box-Pleated Stay-Straight Shades
 Finish: WG · Damp Rated

▶ **1986WG-484 SCONCE** · *Winter Gold*

6"W x 15.50"H x 8"E · Backplate: 6"W x 6"H x 1.50"E
 Ctr/Top: 11.75" Ctr/Btm: 3.75" · 1 – 60 Watt E12 Candelabra
 Decorative White Fabric Box-Pleated Stay-Straight Shade
 Finish: WG · Damp Rated



S484 STAY-STRAIGHT SHADE
 5"W x 5.5"H

▶ **1067WG-101 VANITY** · *Winter Gold*

14.25"W x 10"H x 8"E · Backplate: 6"W x 6"H x 1.50"E
 Ctr/Top: 2.75" Ctr/Btm: 7.50" · 2 – 100 Watt E26
 Medium · Soft White Glass · Finish: WG · Damp Rated



◀ **1068WG-101 VANITY** · *Winter Gold*

23.25"W x 10"H x 8"E
 Backplate: 6"W x 6"H x 1.50"E
 Ctr/Top: 2.75" Ctr/Btm: 7.50" · 3 – 100 Watt
 E26 Medium · Soft White Glass · Finish: WG
 Damp Rated



G101 GLASS
 5.25"W x 5"H

▲ **1069WG-101 VANITY** · *Winter Gold*

32.50"W x 10"H x 8"E
 Backplate: 6"W x 6"H x 1.50"E
 Ctr/Top: 2.75" Ctr/Btm: 7.50" · 4 – 100 Watt E26
 Medium · Soft White Glass · Finish: WG · Damp Rated



fire and ice
collection

IN POLISHED NICKEL
& CAPITAL GOLD



▲ **520881FI FOYER** • *Polished Nickel and Capital Gold*
22"W x 34.75"H • Canopy: 5"W x 1"H • 8 – 60 Watt
E12 Candelabra • Finish: FI • 10' Chain; 15' Wire

Coordinates With

REGAN
119431CG-418-LD
VANITY
see page 277



REGAN
319411CG-437-LD
PENDANT
see page 276



CITY
319201PN PENDANT
see page 131



322041CG PENDANT
see page 417



FI-Polished Nickel & Capital Gold



◀ **62081FI SCONCE** · *Polished Nickel and Capital Gold*
6"W x 18.50"H x 4"E · Backplate: 5"W x 18"H x .75"E
Ctr/Top: 9.25" Ctr/Btm: 9.25" · 1 – 60 Watt E12 Candelabra
Finish: FI · Damp Rated · **ADA**

▶ **320841FI PENDANT** · *Polished Nickel and Capital Gold*
12"W x 16"H · Canopy: 5"W x 1"H · 4 – 60 Watt E12 Candelabra
Finish: FI · 10' Chain; 15' Wire



◀ **220841FI CEILING** · *Polished Nickel and Capital Gold*
18"W x 12"H · Canopy: 5"W x 1"H · 4 – 60 Watt E12 Candelabra
Finish: FI · Damp Rated

► **420861FI CHANDELIER** · *Polished Nickel and Capital Gold*
27"W x 27.50"H · Canopy: 5"W x 1"H · 6 – 60 Watt E12 Candelabra
Finish: FI · 10' Chain; 15' Wire



◄ **520841FI FOYER** · *Polished Nickel and Capital Gold*
17.50"W x 23.75"H · Canopy: 5"W x 1"H · 4 – 60 Watt E12
Candelabra · Finish: FI · 10' Chain; 15' Wire



flynn
collection

IN GUNMETAL



◀ **411061GM-316 CHANDELIER** • *Gunmetal*
 27"W x 24.25"H • Canopy: 5"W x 1"H
 6 – 100 Watt E26 Medium • Soft White Glass
 Finish: GM • 10' Chain; 15' Wire



▲ **511041GM-316 FOYER** • *Gunmetal*
 16"W x 26"H • Canopy: 5"W x .75"H
 4 – 100 Watt E26 Medium • Soft White Glass
 Finish: GM • 10' Chain; 15' Wire



▶ **611011GM-316 SCONCE** • *Gunmetal*
 5"W x 14.25"H x 6.75"E
 Backplate: 5"W x 8.25"H x 1"E
 Ctr/Top: 7" Ctr/Btm: 7.25"
 1 – 100 Watt E26 Medium
 Soft White Glass • Finish: GM
 Damp Rated



▶ **411001GM-316 CHANDELIER** • *Gunmetal*
 36.75"W x 34.25"H • Canopy: 5"W x .75"H
 10 – 60 Watt E26 Medium • Soft White Glass
 Finish: GM • 10' Chain; 15' Wire



GM-Gunmetal



gavin
collection

IN IRON & GOLD

► **421401IG CHANDELIER** · *Iron & Gold*
28"W x 57.50"H · 57.50"H Overall Includes 6", 12" &
18"L Removable Rods · Canopy: 5"W x 1"H · 12 – 60 Watt
E12 Candelabra · Finish: IG · 1' Chain; 6' Wire



◀ **421481IG CHANDELIER** · *Iron & Gold*
16"W x 65.50"H · 65.50"H Overall Includes 6", 12" &
18"L Removable Rods · Canopy: 5"W x 1"H · 8 – 60 Watt
E12 Candelabra · Finish: IG · 1' Chain; 6' Wire



IG-Iron & Gold



▲ **121481IG VANITY** · *Iron & Gold*
30"W x 8.25"H x 4.50"E · Backplate: 7"W x 5"H x 1"E
Ctr/Top: 4.25" Ctr/Btm: 4.25" · 8 – 60 Watt E12
Candelabra · Finish: IG · Damp Rated



▶ **121461IG VANITY** · *Iron & Gold*
21.75"W x 8.25"H x 4.50"E
Backplate: 7"W x 5"H x 1"E
Ctr/Top: 4.25" Ctr/Btm: 4.25"
6 – 60 Watt E12 Candelabra
Finish: IG · Damp Rated



◀ **621461IG SCONCE** · *Iron & Gold*
7"W x 14.25"H x 3.75"E · Backplate: 7"W x 7"H x 1"E
Ctr/Top: 7.50" Ctr/Btm: 6.75" · 6 – 60 Watt E12
Candelabra · Finish: IG · Damp Rated

Coordinates With

312811GM PENDANT

see page 463



**NASH
213211GM-LD CEILING**

see page 247



**EASTMAN
4883SZ PENDANT**

see page 151



▲ **421402IG CHANDELIER** · *Iron & Gold*
36.50"W x 59.25"H · 59.25"H Overall Includes 6",
12" & 18"L Removable Rods · Canopy: 5"W x 1"H
12 – 60 Watt E12 Candelabra · Finish: IG
1' Chain; 6' Wire



◀ **4494SQ-569-CR PETITE** • *Silver Quartz*
17"W x 21.25"H • Canopy: 5"W x .75"H • 4 – 60 Watt E12
Candelabra • Decorative White Fabric Shade • Finish: SQ
Crystals Included • 10' Chain; 15' Wire

▼ **4491SQ-570-CR SCONCE** • *Silver Quartz*
8.50"W x 13.25"H x 9.75"E • Backplate: 5"W x 5"H x .75"E
Ctr/Top: 7.25" Ctr/Btm: 6" • 1 – 60 Watt E26 Medium
Decorative White Fabric Stay-Straight Shade • Finish: SQ
Crystals Included • Damp Rated



harlow

collection

IN SILVER QUARTZ



▲ **4492SQ-571-CR SCONCE** • *Silver Quartz*
26"W x 11.75"H x 9.25"E • Backplate: 5"W x 5"H x .75"E
Ctr/Top: 3.75" Ctr/Btm: 8" • 2 – 60 Watt E26 Medium
Decorative White Fabric Shades • Finish: SQ • Crystals
Included • Damp Rated



◀ **4496SQ-000-CR CHANDELIER** · *Silver Quartz*
25.5"W x 27.5"H · Canopy: 5"W x .75"H · 6 – 60 Watt
E12 Candelabra · Finish: SQ · Crystals Included
10' Chain; 15' Wire

▶ **4499SQ-000-CR CHANDELIER** · *Silver Quartz*
32.25"W x 36.5"H · Canopy: 5"W x .75"H · 9 – 60 Watt
E12 Candelabra · Finish: SQ · Crystals Included
10' Chain; 15' Wire




SQ-Silver Quartz



◀ **3561BB-252 PENDANT** • *Burnished Bronze*
6"W x 46"H • 46"H Overall Includes 6", 12" & 18"L
Removable Rods • Canopy: 5.50"W x 2.50"H
1 – 100 Watt E26 Medium • Mist Scavo Glass
Finish: BB • 1' Chain; 6' Wire

▶ **2273BB CEILING** • *Burnished Bronze*
13.75"W x 8"H • 2 – 60 Watt E26 Medium
Mist Scavo Glass • Finish: BB • Damp Rated



hill
house
collection

IN BURNISHED BRONZE



◀ **3563BB CEILING** • *Burnished Bronze*
16.25"W x 16.25"H • Canopy: 5.75"W x 2.25"H
2 – 100 Watt E26 Medium • Mist Scavo Glass
Finish: BB • Damp Rated



◀ **1886BB-252 SCONCE** • *Burnished Bronze*
6"W x 12.50"H x 7"E • Backplate: 5.75"W x 8.75"H x 1"E
Ctr/Top: 8.50" Ctr/Btm: 4" • 1 – 100 Watt E26 Medium
Mist Scavo Glass • Finish: BB • Damp Rated

▶ **3569BB-252 CHANDELIER** • *Burnished Bronze*
33"W x 36.50"H • Canopy: 6.25"W x 2"H • 9 – 60 Watt
E26 Medium • Mist Scavo Glass • Finish: BB • 10' Chain;
15' Wire



▶ **3564BB PENDANT** • *Burnished Bronze*
21"W x 30"H • Canopy: 5.25"W x 1.75"H • 3 – 100 Watt
E26 Medium • Mist Scavo Glass • Finish: BB • 10' Chain;
15' Wire



◀ **3566BB-252 CHANDELIER** • *Burnished Bronze*
28"W x 28"H • Canopy: 5.25"W x 1.75"H • 6 – 100 Watt
E26 Medium • Mist Scavo Glass • Finish: BB • 10' Chain;
15' Wire



G252 GLASS
6"W x 5.25"H
Mist Scavo



▶ **1882BB-252 VANITY** • *Burnished Bronze*

18"W x 11"H x 7"E

Backplate: 8.75"W x 5.75"H x 1"E • Ctr/Top: 2.50"

Ctr/Btm: 8.50" • 2 – 100 Watt E26 Medium

Mist Scavo Glass • Finish: BB • Damp Rated



◀ **1883BB-252 VANITY** • *Burnished Bronze*

23.50"W x 11"H x 7"E

Backplate: 8.75"W x 5.75"H x 1"E

Ctr/Top: 2.50" Ctr/Btm: 8.50" • 3 – 100 Watt

E26 Medium • Mist Scavo Glass • Finish: BB
Damp Rated

▼ **1884BB-252 VANITY** • *Burnished Bronze*

31"W x 11"H x 7"E


Backplate: 8.75"W x 5.75"H x 1"E

Ctr/Top: 2.50" Ctr/Btm: 8.50" • 4 – 100 Watt

E26 Medium • Mist Scavo Glass • Finish: BB
Damp Rated



► **411901PN CHANDELIER** • *Polished Nickel*
37.50"W x 32.25"H • Canopy: 5"W x 1"H • 10 – 60 Watt
E12 Candelabra • Finish: PN • Clear Glass Column &
Adornments • 10' Chain; 15' Wire



hudson

collection


IN POLISHED NICKEL



◀ **411961PN CHANDELIER** • *Polished Nickel*
26"W x 23.50"H • Canopy: 5"W x 1"H • 6 – 60 Watt
E12 Candelabra • Finish: PN • Clear Glass Column &
Adornments • 10' Chain; 15' Wire



◀ **611911PN SCONCE** · *Polished Nickel*
 6"W x 20.50"H x 5.25"E
 Backplate: 5.75"W x 6.50"H x .75"E
 Ctr/Top: 3.75" Ctr/Btm: 16.75"
 1 – 60 Watt E12 Candelabra
 Decorative White Fabric Shade · Finish: WG
 Clear Glass · Damp Rated



SH682 SHADE
 6"W x 7.25"H

Coordinates With

511441PN FOYER
 see page 433




214141PN CEILING
 see page 411



▶ **411902PN CHANDELIER** · *Polished Nickel*
 60"W x 49"H · Canopy: 5"W x 1"H · 16 – 60 Watt
 E12 Candelabra · Finish: PN · Clear Glass Column &
 Adornments · 10' Chain; 15' Wire

50+LBS

Additional mounting support required





▲ **4261WG-552 SCONCE** · *Winter Gold*
6.75"W x 12.50"H x 8.75"E · Backplate: 5.25"W x 5.25"H x 1"E
Ctr/Top: 9.50" Ctr/Btm: 3" · 1 - 60 Watt G16 Round
Decorative White Fabric Stay-Straight Shade
Finish: WG · K9 Crystal · Damp Rated

▶ **4263WG-552 CHANDELIER** · *Winter Gold*
20"W x 18.75"H · Canopy: 5.25"W x 1"H
3 - 60 Watt G16 Round · Decorative White
Fabric Stay-Straight Shades · Finish: WG
K9 Crystals · 10' Chain; 15' Wire



hutton

collection

IN WINTER GOLD




◀ **4264WG-568 CHANDELIER** · *Winter Gold*
19.25"W x 21.50"H · Canopy: 5.25"W x 1"H · 4 - 60
Watt E12 Candelabra · Decorative White Fabric Shade
Finish: WG · K9 Crystals · 10' Chain; 15' Wire



◀ **4266WG-552 CHANDELIER** • *Winter Gold*
29"W x 25.75"H • Canopy: 5.25"W x 1"H • 6 - 60 Watt G16
Round • Decorative White Fabric Stay-Straight Shades
Finish: WG • K9 Crystals • 10' Chain; 15' Wire

▶ **4269WG-552 CHANDELIER** • *Winter Gold*
34"W x 31.50"H • Canopy: 5.25"W x 1"H • 9 - 60 Watt G16
Round • Decorative White Fabric Stay-Straight Shades
Finish: WG • K9 Crystals • 10' Chain; 15' Wire





jackson
collection

IN OIL RUBBED BRONZE




◀ **4896OR PENDANT** · *Oil Rubbed Bronze*
32"W x 23.50"H · Canopy: 6"W x 1"H · 6 – 100 Watt
E26 Medium · Finish: OR · 10' Chain; 15' Wire

▶ **4894OR PENDANT** · *Oil Rubbed Bronze*
21.75"W x 12.50"H · Canopy: 5"W x 1"H
4 – 100 Watt E26 Medium · Frosted Glass Diffuser
with Finial · Finish: OR · 10' Chain; 15' Wire




▼ **4892OR SCONCE** • *Oil Rubbed Bronze*

12"W x 10.50"H x 5.25"E
 Backplate: 6.25"W x 10.50"H x 1"E
 Ctr/Top: 5.25" Ctr/Btm: 5.25" • 2 – 100 Watt E26 Medium
 Finish: OR • Damp Rated




▲ **4897OR SCONCE** • *Oil Rubbed Bronze*

7.25"W x 17.75"H x 5"E
 Backplate: 7.25"W x 17.75"H x 1"E
 Ctr/Top: 9" Ctr/Btm: 9" • 1 – 100 Watt E26 Medium
 Finish: OR • Damp Rated



▼ **4893OR VANITY** • *Oil Rubbed Bronze*

19.75"W x 8"H x 4.75"E
 Backplate: 19.75"W x 8"H x .75"E
 Ctr/Top: 4" Ctr/Btm: 4" • 3 – 100 Watt E26 Medium
 Finish: OR • Damp Rated



▲ **4899OR SCONCE** • *Oil Rubbed Bronze*

7.25"W x 8"H x 5"E • Backplate: 7.25"W x 8"H x 1"E
 Ctr/Top: 4" Ctr/Btm: 4" • 1 – 100 Watt E26 Medium
 Finish: OR • Damp Rated



▲ **4891OR SCONCE** · *Oil Rubbed Bronze*
 5"W x 13.25"H x 6.75"E
 Backplate: 4.50"W x 7.50"H x .75"E
 Ctr/Top: 4.25" Ctr/Btm: 9" · 1 – 100 Watt E26 Medium
 Finish: OR · Damp Rated

▼ **4895OR CEILING** · *Oil Rubbed Bronze*
 15.75"W x 8"H · 3 – 60 Watt E26 Medium · Frosted
 Glass Diffuser with Finial · Finish: OR · Damp Rated



▲ **4898OR PENDANT** · *Oil Rubbed Bronze*
 15"W x 20.50"H · Canopy: 5"W x 1"H
 4 – 100 Watt E26 Medium · Finish: OR
 10' Chain; 15' Wire



▲ **4890OR PENDANT** · *Oil Rubbed Bronze*
 8"W x 64.25"H · 64.25"H Overall Includes 6", 12" & 18"L
 Removable Rods · Canopy: 5"W x 1"H · 1 – 100 Watt E26
 Medium · Finish: OR · 1' Chain; 6' Wire



juliette

collection

IN WINTER GOLD



▼ **312162WG PENDANT** • *Winter Gold*
26"W x 30.25"H • Canopy: 5"W x 1"H
6 – 60 Watt E12 Candelabra • Finish: WG
Includes Crystals • 10' Chain; 15' Wire



Coordinates With

CAMBRIDGE
413601WG CHANDELIER
see page 93



◀ **312161WG PENDANT** • *Winter Gold*
22.50"W x 29"H • Canopy: 5"W x 1"H
6 – 60 Watt E12 Candelabra • Finish: WG
Includes Crystals • 10' Chain; 15' Wire



▲ **312141WG PETITE** • *Winter Gold*
15"W x 23"H • Canopy: 5"W x .75"H • 4 – 60 Watt
E12 Candelabra • Finish: WG • Includes Crystals
10' Chain; 15' Wire



G299 GLASS
5.375"W x 4.75"H

▼ **118721DS-299 VANITY** · *Dark Spice*
14.75"W x 9"H x 7.75"E
Backplate: 5"W x 5"H x .75"E Ctr/Top: 5"
Ctr/Btm: 4" · 2 – 100 Watt E26 Medium · Soft
White Glass · Finish: DS · Damp Rated

▲ **118731DS-299 VANITY** · *Dark Spice*
23"W x 9"H x 7.75"E
Backplate: 5"W x 5"H x .75"E · Ctr/Top: 5"
Ctr/Btm: 4" · 3 – 100 Watt E26 Medium · Soft
White Glass · Finish: DS · Damp Rated



kingsley
collection
IN DARK SPICE



SH668 SHADE
10.50"W x
7"H x 4.25"E



▲ **618721DS-668 SCONCE** · *Dark Spice*
10.50"W x 17"H x 4.25"E
Backplate: 10"W x 7"H x .75"E · Ctr/Top: 3.50"
Ctr/Btm: 13.50" · 2 – 60 Watt E12 Candelabra
Decorative White Fabric Shade · Finish: DS · Damp Rated



▲ **118741DS-299 VANITY** · *Dark Spice*
31.50"W x 9"H x 7.75"E · Backplate: 5"W x 5"H x .75"E
Ctr/Top: 5" Ctr/Btm: 4" · 4 – 100 Watt E26 Medium
Soft White Glass · Finish: DS · Damp Rated



► **518741DS FOYER** • *Dark Spice*
17.75"W x 30.25"H • Canopy: 5"W x 1"H
4 – 60 Watt E12 Candelabra
Finish: DS • 10' Chain; 15' Wire



▲ **418761DS CHANDELIER** • *Dark Spice*
29.75"W x 32.25"H • Canopy: 5"W x 1"H • 6 – 60 Watt
E12 Candelabra • Finish: DS • 10' Chain; 15' Wire

► **418701DS CHANDELIER** • *Dark Spice*
36"W x 43"H • Canopy: 5"W x 1"H • 10 – 60 Watt E12
Candelabra • Finish: DS • 10' Chain; 15' Wire





knox
collection

IN OLD BRONZE

Coordinates With


**DYLAN
9568OB PENDANT**
see page 363



317911OB PENDANT
see page 470



▼ **420301OB CHANDELIER** · *Old Bronze*
38"W x 39"H · Canopy: 5"W x 1"H · 12 – 60 Watt
E12 Candelabra · Finish: OB · 10' Chain; 15' Wire



▲ **120331OB-435 VANITY** · *Old Bronze*

25"W x 8.75"H x 7"E · Backplate: 8"W x 4.75"H x .75"E
Ctr/Top: 2.25" Ctr/Btm: 6.50" · 3 – 100 Watt E26
Medium · Clear Seeded Glass · Finish: OB · Damp Rated



▼ **620311OB-421 SCONCE** · *Old Bronze*

8.25"W x 14.75"H x 10.25"E
Backplate: 4.75"W x 8"H x .75"E · Ctr/Top: 4.25"
Ctr/Btm: 10.50" · 1 – 100 Watt E26 Medium · Clear
Seeded Glass · Finish: OB · Damp Rated



▶ **420361OB CHANDELIER** · *Old Bronze*

29.25"W x 30"H · Canopy: 5"W x 1"H · 6 – 60 Watt
E12 Candelabra · Finish: OB · 10' Chain; 15' Wire



► **512431OB FOYER** • *Old Bronze*
 12"W x 21"H • Canopy: 5"W x .75"H • 3 – 60 Watt E12
 Candelabra • Finish: OB • 10' Chain; 15' Wire



◄ **512441OB FOYER** • *Old Bronze*
 15"W x 25.50"H • Canopy: 5"W x .75"H • 4 – 60 Watt E12
 Candelabra • Finish: OB • 10' Chain; 15' Wire



► **512462OB FOYER** • *Old Bronz*
 20"W x 30"H • Canopy: 5"W x .75"H • 6 – 60 Watt
 E12 Candelabra • Finish: OB • 10' Chain; 15' Wire



leigh
collection

IN BURNISHED BRONZE

► **4701BB-000 SCONCE** • *Burnished Bronze*
5.75"W x 14"H x 5.25"E
Mirror Backplate: 4.25" W x 11.75" H x 1"E
Ctr/Top: 6.75" Ctr/Btm: 7.25" • 1 – 60 Watt E12
Candelabra • Finish: BB • Damp Rated



◄ **4709BB-000 CHANDELIER** • *Burnished Bronze*
34"W x 34.25"H • Canopy: 5"W x 1"H • 9 – 60 Watt E12
Candelabra • Finish: BB • K9 Crystal • 10' Chain; 15' Wire



► **4705BB FOYER** • *Burnished Bronze*
16"W x 27"H • Canopy: 5"W x 1"H • 4 – 60 Watt
E12 Candelabra • Finish: BB • K9 Crystal
10' Chain; 15' Wire



◀ **4704BB FOYER** • *Burnished Bronze*
10.50"W x 19.75"H • Canopy: 5"W x 1"H
4 – 60 Watt E12 Candelabra • Finish: BB
K9 Crystal • 10' Chain; 15' Wire

4704BB FOYER

Includes Flush
Mount Option
10.5"W x
18.5"H





◀ **8113BB-300 VANITY** · *Burnished Bronze*

22.50"W x 9.50"H x 6.25"E

Backplate: 7.25"W x 5"H x 1"E

Ctr/Top: 3.75 Ctr/Btm: 6" · 3 – 100 Watt

E26 Medium · Cased Opal Glass

Finish: BB · Damp Rated



G300 GLASS

5.5"W x 5.5"H

▶ **4706BB-000 CHANDELIER** · *Burnished Bronze*

26.25"W x 28"H · Canopy: 5"W x 1"H · 6 – 60 Watt E12

Candelabra · Finish: BB · K9 Crystal · 10' Chain; 15' Wire





loft
collection

IN BURNISHED BRONZE
& MATTE NICKEL



◀ **3926MN-630 ISLAND** • *Matte Nickel*
38"W x 46"H x 16"E • 46"H Overall • Includes 6",
12" & 18"L Removable Rods • Canopy: 7"W x 1.5"H
6 – 60 Watt E12 Candelabra • Frosted Glass Diffuser
with Finial • Decorative White Fabric Shade
Finish: MN • 1' Chain; 6' Wire

▶ **3926BB-629 ISLAND** • *Burnished Bronze*
38"W x 46"H x 16"E • 46"H Overall • Includes 6",
12" & 18"L Removable Rods • Canopy: 7"W x 1.5"H
6 – 60 Watt E12 Candelabra • Frosted Glass Diffuser
with Finial • Decorative Light Tan Fabric Shade • Finish: BB •
1' Chain; 6' Wire



► **3925BB-469 CHANDELIER** · *Burnished Bronze*
 26.50"W x 24.50"H · Canopy: 4.75"W x 1.5"H · 5 – 60 Watt
 E12 Candelabra · Decorative White Fabric Stay-Straight
 Shades · Finishes: BB, MN · 10' Chain; 15' Wire



▲ **3925BB-468 CHANDELIER** · *Burnished Bronze*
 26.50"W x 24.50"H · Canopy: 4.75"W x 1.5"H · 5 – 60 Watt
 E12 Candelabra · Decorative Tan Fabric Stay-Straight
 Shades · Finish: BB · 10' Chain; 15' Wire



► **3925MN-469 CHANDELIER** · *Matte Nickel*
 26.50"W x 24.50"H · Canopy: 4.75"W x 1.5"H · 5 – 60 Watt
 E12 Candelabra · Decorative White Fabric Stay-Straight
 Shades · Finishes: BB, MN · 10' Chain; 15' Wire

◀ **3922BB-613 PENDANT** · *Burnished Bronze*

Finish: BB · Decorative Light Tan Fabric Shade

▶ **3922MN-623 PENDANT** · *Matte Nickel*

Finish: MN · Decorative White Fabric Shade

24"W x 50.50"H · 50.50"H Overall Includes 6",
12" & 18"L Removable Rods · Canopy: 6"W x 1"H
4 – 60 Watt E26 Medium · Frosted Glass Diffuser
with Finial · 1' Chain; 6' Wire



▲ **3923BB-480 CEILING** · *Burnished Bronze*

Finishes: BB, MN · Decorative White Fabric Shade

▲ **3923MN-480 CEILING** · *Matte Nickel*

Finishes: BB, MN · Decorative White Fabric Shade

▶ **3923BB-479 CEILING** · *Burnished Bronze*

Finish: BB · Decorative Tan Fabric Shade

15.25"W x 11.25"H · Canopy: 4.80"W x 1.50"H · 3 – 60 Watt
E26 Medium · Frosted Glass Diffuser with Finial · Damp Rated



◀ **1981BB-469 SCONCE** · *Burnished Bronze*

Finishes: BB, MN · Decorative White Fabric Shade

◀ **1981MN-469 SCONCE** · *Matte Nickel*

Finishes: BB, MN · Decorative White Fabric Shade

◀ **1981BB-468 SCONCE** · *Burnished Bronze*

Finish: BB · Decorative Tan Fabric Shade

6"W x 14.50"H x 7"E ·

Backplate: 5"W x 8.75"H x .50"E · Ctr/Top: 10"

Ctr/Btm: 4.50" · 1 – 60 Watt E12 Candelabra

Damp Rated



lowell
collection

IN TUSCAN BRONZE

▼ **4796TZ PENDANT** • *Tuscan Bronze*
 24"W x 30"H • Canopy: 5"W x 1"H • 6 – 60 Watt E12
 Candelabra • Decorative Wood Beads • Finish: TZ
 10' Chain; 15' Wire



▲ **4794TZ PENDANT** • *Tuscan Bronze*
 18.25"W x 23.75"H • Canopy: 5"W x 1"H
 4 – 60 Watt E12 Candelabra • Decorative
 Wood Beads • Finish: TZ • 10' Chain; 15' Wire

▲ **4793TZ PENDANT** • *Tuscan Bronze*
 13.50"W x 19"H • Canopy: 5"W x 1"H
 3 – 60 Watt E12 Candelabra • Decorative Wood
 Beads • Finish: TZ • 10' Chain; 15' Wire



▼ **4795TZ CEILING** • *Tuscan Bronze*
 15"W x 14.50"H • Canopy: 5"W x 1"H
 3 – 60 Watt E12 Candelabra • Decorative Wood
 Beads • Finish: TZ

▶ **3938WG-475 CHANDELIER** · *Winter Gold*
30"W x 70.50"H · 70.50"H Overall Includes 6", 12" &
18"L Removable Rods · Canopy: 5"W x 1"H
8 – 60 Watt E12 Candelabra · Mica Shade
Finish: WG · 1' Chain; 6' Wire

▼ **1027WG-410 SCONCE** · *Winter Gold*
17"W x 12.75"H x 8.75"E
Backplate: 5"W x 7.75"H x 1.25"E · Ctr/Top: 8.75"
Ctr/Btm: 4" · 2 – 60 Watt E12 Candelabra
Mica Stay-Straight Shades · Finish: WG



luna
collection
IN WINTER GOLD



▲ **1026WG-410 SCONCE** · *Winter Gold*
7"W x 12.75"H x 8.50"E
Backplate: 5"W x 7.75"H x 1.25"E · Ctr/Top: 8.75"
Ctr/Btm: 4" · 1 – 60 Watt E12 Candelabra
Mica Stay-Straight Shade · Finish: WG

▲ **3933WG-476 CEILING** · *Winter Gold*
17"W x 13"H · Canopy: 6"W x 1.50"H
3 – 60 Watt E26 Medium · Frosted Acrylic Diffuser
with Finial · Mica Shade · Finish: WG



◀ **3936WG-470 CHANDELIER** · *Winter Gold*
 30"W x 32.5"H · Canopy: 5"W x 1"H · 6 – 60 Watt E12
 Candelabra · Mica Stay-Straight Shades · Finish: WG
 10' Chain; 15' Wire



▲ **1017WG-526 SCONCE** · *Winter Gold*
 11.50"W x 10"H x 4"E
 Backplate: 10.50"W x 8"H x .75"E
 Ctr/Top: 5" Ctr/Btm: 5" · 2 – 60 Watt E12
 Candelabra · Mica Shade · Finish: WG
ADA



◀ **1008WG-410 VANITY** · *Winter Gold*
 26.50"W x 8.50"H x 8.75"E
 Backplate: 7.75"W x 5"H x 1.25"E
 Ctr/Top: 5.75" Ctr/Btm: 2.75" · 3 – 60 Watt
 E12 Candelabra · Mica Stay-Straight Shades
 Finish: WG

▼ **1009WG-410 VANITY**
Winter Gold
 36.25"W x 8.50"H x 8.75"E
 Backplate: 7.75"W x 5"H x 1.25"E
 Ctr/Top: 5.75" Ctr/Btm: 2.75"
 4 – 60 Watt E12 Candelabra
 Mica Stay-Straight Shades
 Finish: WG

▶ **1007WG-410 VANITY**
Winter Gold
 17"W x 8.50"H x 8.75"E
 Backplate: 7.75"W x 5"H x 1.25"E
 Ctr/Top: 5.75" Ctr/Btm: 2.75"
 2 – 60 Watt E12 Candelabra
 Mica Stay-Straight Shades
 Finish: WG






manhattan
collection

IN POLISHED NICKEL

► **420661PN-423 CHANDELIER** · *Polished Nickel*
 28"W x 29.50"H · Canopy: 5"W x .75"H · 6 – 100 Watt
 E26 Medium · Clear Beveled Glass · Finish: PN · Clear
 Glass Column · 10' Chain; 15' Wire




◄ **520661PN FOYER** · *Polished Nickel*
 22"W x 37.50"H · Canopy: 5"W x .75"H · 6 – 60 Watt
 E12 Candelabra · Finish: PN · Clear Glass Column
 10' Chain; 15' Wire



◄ **620611PN-423 SCONCE** · *Polished Nickel*
 5.25"W x 17.50"H x 7"E
 Backplate: 5.25"W x 10"H x 1.25"E · Ctr/Top:
 10.25" Crt/Btm: 7.25" · 1 – 100 Watt E26 Medium
 Clear Beveled Glass · Finish: PN · Damp Rated



► **520641PN FOYER** · *Polished Nickel*
 15"W x 27.50"H · Canopy: 5"W x .75"H · 4 – 60 Watt
 E12 Candelabra · Finish: PN · Clear Glass Column
 10' Chain; 15' Wire



GL423
 4"W x 6.25"H



margo
collection

IN WINTER GOLD



◀ **4226WG-549-CR CHANDELIER** • *Winter Gold*
 30"W x 23"H • Canopy: 5"W x 1"H
 6 – 60 Watt E12 Candelabra • Decorative
 White Fabric Stay-Straight Shades
 Finish: WG • Includes Crystals
 6' Chain; 10' Wire



▶ **4224WG-551-CR PENDANT** • *Winter Gold*
 20"W x 18.25"H • Canopy: 5"W x 1"H • 4 – 60 Watt E12
 Candelabra • Decorative White Fabric Shade • Finish: WG
 Includes Crystals • 6' Chain; 10' Wire



S549
 6.75"W x 3.25"H
 Stay-Straight
 Shade

**4224WG-551-CR
 PENDANT**
 Includes
 Semi-Flush
 Mount Option
 20"W x 18"H



◀ **4229WG-549-CR CHANDELIER** • *Winter Gold*
 34"W x 29"H • Canopy: 5"W x 1"H • 9 – 60 Watt E12
 Candelabra • Decorative White Fabric Stay-Straight Shades
 Includes Crystals • Finish: WG • 6' Chain; 10' Wire



▲ **4221WG-549-CR SCONCE** • *Winter Gold*
 6.75"W x 10.50"H x 8"E
 Backplate: 5"W x 5"H x .75"E • Ctr/Top: 6.25"
 Ctr/Btm: 4.25" • 1 – 60 Watt E12 Candelabra
 Decorative White Fabric Stay-Straight Shade
 Finish: WG • Includes Crystal • Damp Rated



◀ **4531CB-000 SCONCE** · *Chesterfield Brown*
9"W x 15.75"H x 5.50"E · Backplate: 5"W x 5"H x 1"E
Ctr/Top: 12.50" Ctr/Btm: 3.25" · 2 – 60 Watt E12
Candelabra · Finish: CB · Damp Rated

maxwell

collection

IN CHESTERFIELD BROWN



▶ **4533CB CEILING** · *Chesterfield Brown*
15.25"W x 13.75"H · 3 – 60 Watt E12 Candelabra
Finish: CB

▼ **4536CB-000 CHANDELIER** · *Chesterfield Brown*
28"W x 33"H · Canopy: 5"W x 1"H · 6 – 60 Watt E12
Candelabra · Finish: CB · 10' Chain; 15' Wire



CB-Chesterfield Brown

Coordinates With

**WYATT
9001SY FOYER**
see page 340



**WYATT
4253SY CEILING**
see page 338



**WYATT
8012SY-123 VANITY**
see page 341





◀ **321243WG-CR PENDANT** • *Winter Gold*
26.25"W x 31"H • Canopy: 5"W x .75"H • 4 – 60 Watt
E12 Candelabra • Finish: WG • Includes Crystals • 10'
Chain; 15' Wire

merc
er
collection

IN WINTER GOLD



◀ **321242WG PENDANT** • *Winter Gold*
25.25"W x 25.50"H • Canopy: 5"W x .75"H
4 – 60 Watt E12 Candelabra • Finish: WG
10' Chain; 15' Wire



▶ **321241WG PENDANT** • *Winter Gold*
18"W x 19.50"H • Canopy: 5"W x .75"H • 4 – 60 Watt
E12 Candelabra • Finish: WG • 10' Chain; 15' Wire



◀ **421201WG CHANDELIER** · *Winter Gold*
 36"W x 29.25"H · Canopy: 5"W x .75"H · 10 – 60 Watt
 E12 Candelabra · Finish: WG · 10' Chain; 15' Wire

▼ **421261WG CHANDELIER** · *Winter Gold*
 28.50"W x 23.25"H · Canopy: 5"W x .75"H · 6 – 60 Watt
 E12 Candelabra · Finish: WG · 10' Chain; 15' Wire



SH654 SHADE
 6"W x 4.75"H
 Stay-Straight

◀ **621212WG-654 SCONCE** · *Winter Gold*
 6"W x 22.25"H x 7"E · Backplate: 4.75"W x 8"H x .75"E
 Ctr/Top: 11.25" Ctr/Btm: 11" · 1 – 60 Watt E12
 Candelabra · Decorative White Fabric Stay-Straight
 Shade · Finish: WG · Damp Rated

▶ **621211WG-CR-671 SCONCE** · *Winter Gold*
 5"W x 20.50"H x 6.50"E · Backplate: 5"W x 5"H x 1"E
 Ctr/Top: 9.75" Ctr/Btm: 10.75" · 1 – 60 Watt E12
 Candelabra · Decorative White Fabric Stay-Straight
 Shade · Finish: WG · Includes Crystal · Damp Rated



SH671 SHADE
 5"W x 5"H
 Stay-Straight



WG-Winter Gold



mid-
century
collection


IN AGED BRASS
& POLISHED NICKEL

mid-century | IN AGED BRASS & POLISHED NICKEL

► **821151AD-426 ISLAND** • *Aged Brass*
47"W x 58.75"H x 10"E • 58.75"H Overall
Includes 6", 12" & 18"L Removable Rods • Canopy:
13"L x 5"W x 1"H • 5 – 100 Watt E26 Medium
Clear Glass • Finishes: AD, PN • 1' Chain; 6' Wire



◄ **821151PN-426 ISLAND** • *Polished Nickel*
47"W x 58.75"H x 10"E • 58.75"H Overall
Includes 6", 12" & 18"L Removable Rods • Canopy:
13"L x 5"W x 1"H • 5 – 100 Watt E26 Medium
Clear Glass • Finishes: AD, PN • 1' Chain; 6' Wire



Coordinates With

ZANDER
621931PN SCONCE
see page 344



ZANDER
621931AD SCONCE
see page 344





◀ **321151AD-426 PENDANT** · *Aged Brass*
 21.50"W x 64.25"H · 64.25" Overall Includes 6",
 12" & 18"L Removable Rods for each light (total
 of 15 rods) · Canopy: 18.5"W x 1.75"H · 5 – 100
 Watt E26 Medium Clear Glass · Finishes: AD, PN
 1' Chain; 6' Wire

▶ **321151PN-426 PENDANT** · *Polished Nickel*
 21.50"W x 64.25"H · 64.25" Overall Includes 6",
 12" & 18"L Removable Rods for each light (total
 of 15 rods) · Canopy: 18.5"W x 1.75"H · 5 – 100
 Watt E26 Medium · Clear Glass · Finishes: AD, PN
 1' Chain; 6' Wire



**321111AD
 PENDANT**
 Includes
 Semi-Flush Option
 11.25"W x 15"H



**321111PN
 PENDANT**
 Includes
 Semi-Flush Option
 11.25"W x 15"H



◀ **321111AD PENDANT** · *Aged Brass*
 ▶ **321111PN PENDANT** · *Polished Nickel*
 11.25"W x 50.75"H · 50.75"H Overall Includes 6",
 12" & 18"L Removable Rods · Canopy: 5"W x .75"H
 1 – 100 Watt E26 Medium · Clear Glass · Finishes:
 AD, PN · 1' Chain; 6' Wire

mid-century | IN AGED BRASS & POLISHED NICKEL



◀ **421161AD-426 CHANDELIER** · *Aged Brass*
29.50"W x 67.50"H · 67.50"H Overall Includes 6",
12" & 18"L Removable Rods · Canopy: 5"W x .75"H
6 – 100 Watt E26 Medium · Clear Glass
Finishes: AD, PN · 1' Chain; 6' Wire

▶ **421161PN-426 CHANDELIER** · *Polished Nickel*
29.50"W x 67.50"H · 67.50"H Overall Includes 6",
12" & 18"L Removable Rods · Canopy: 5"W x .75"H
6 – 100 Watt E26 Medium · Clear Glass · Finishes:
AD, PN · 1' Chain; 6' Wire



◀ **421141AD-426 CHANDELIER** · *Aged Brass*
17.25"W x 65"H · 65"H Overall Includes 6", 12" & 18"
Removable Rods · Canopy: 5"W x .75"H · 4 – 100 Watt E26
Medium · Clear Glass · Finishes: AD, PN · 1' Chain; 6' Wire



▶ **421141PN-426 CHANDELIER** · *Polished Nickel*
17.25"W x 65"H · 65"H Overall Includes 6", 12" & 18"
Removable Rods · Canopy: 5"W x .75"H · 4 – 100 Watt E26
Medium · Clear Glass · Finishes: AD, PN · 1' Chain; 6' Wire



mid-century | IN AGED BRASS & POLISHED NICKEL



◀ **421101AD-426 CHANDELIER** · *Aged Brass*
35.75"W x 75"H · 75"H Overall Includes 6", 12" & 18"L
Removable Rods · Canopy: 5"W x .75"H · 10 – 100 Watt
E26 Medium · Clear Glass · Finishes: AD, PN
1' Chain; 6' Wire


▶ **421101PN-426 CHANDELIER** · *Polished Nickel*
35.75"W x 75"H · 75"H Overall Includes 6", 12" & 18"L
Removable Rods · Canopy: 5"W x .75"H · 10 – 100 Watt
E26 Medium · Clear Glass · Finishes: AD, PN
1' Chain; 6' Wire



◀ **321142AD PENDANT** · *Aged Brass*
◀ **321142PN PENDANT** · *Polished Nickel*
15.50"W x 65"H · 65"H Overall Includes 6", 12" & 18"L
Removable Rods · Canopy: 5"W x .75"H · 4 – 60 Watt
E12 Candelabra · Clear Glass · Finishes: AD, PN
1' Chain; 6' Wire



mid-century | IN AGED BRASS & POLISHED NICKEL



▲ **121121AD-426 VANITY** · *Aged Brass*
 ▲ **121121PN-426 VANITY** · *Polished Nickel*

14.50"W x 9.75"H x 6.75"E
 Backplate: 5.25"W x 5.25"H x 1"E · Ctr/Top:
 2.75" Ctr/Btm: 7" · 2 – 100 Watt E26 Medium
 Clear Glass · Finishes: AD, PN · Damp Rated

▲ **121131AD-426 VANITY** · *Aged Brass*
 23.50"W x 9.75"H x 6.75"E · Backplate: 5.25"W x 5.25"H x 1"E
 Ctr/Top: 7" Ctr/Btm: 2.75" · 3 – 100 Watt E26 Medium · Clear
 Glass · Finishes: AD, PN · Damp Rated

► **121131PN-426 VANITY** · *Polished Nickel*
 23.50"W x 9.75"H x 6.75"E · Backplate: 5.25"W x 5.25"H x 1"E
 Ctr/Top: 2.75" Ctr/Btm: 7" · 3 – 100 Watt E26 Medium
 Clear Glass · Finishes: AD, PN · Damp Rated



GL426
 5.75"W x 5"H

▲ **121141AD-426 VANITY** · *Aged Brass*
 32"W x 9.75"H x 6.75"E · Backplate: 5.25"W x 5.25"H x 1"E
 Ctr/Top: 2.75" Ctr/Btm: 7" · 4 – 100 Watt E26 Medium
 Clear Glass · Finishes: AD, PN · Damp Rated



▲ **121141PN-426 VANITY** · *Polished Nickel*
 32"W x 9.75"H x 6.75"E · Backplate: 5.25"W x 5.25"H x 1"E
 Ctr/Top: 2.75" Ctr/Btm: 7" · 4 – 100 Watt E26 Medium
 Clear Glass · Finishes: AD, PN · Damp Rated



midtown

collection

IN BURNISHED BRONZE,
MATTE NICKEL
& POLISHED NICKEL



◀ **3915BB-454 CHANDELIER** · *Burnished Bronze*
25"W x 25.75"H · Canopy: 5"W x 1"H · 5 – 60 Watt E12
Candelabra · Decorative Tan Fabric Shade · Finish: BB
10' Chain; 15' Wire

▶ **3915BB-455 CHANDELIER** · *Burnished Bronze*
25"W x 25.75"H · Canopy: 5"W x 1"H · 5 – 60 Watt E12
Candelabra · Decorative White Fabric Shade · Finishes:
BB, MN, PN · 10' Chain; 15' Wire



◀ **3915PN-455 CHANDELIER** · *Polished Nickel*
25"W x 25.75"H · Canopy: 5"W x 1"H · 5 – 60 Watt E12
Candelabra · Decorative White Fabric Shade · Finishes:
BB, MN, PN · 10' Chain; 15' Wire



▶ **3915MN-455 CHANDELIER** · *Matte Nickel*
25"W x 25.75"H · Canopy: 5"W x 1"H · 5 – 60 Watt E12
Candelabra · Decorative White Fabric Shade · Finishes:
BB, MN, PN · 10' Chain; 15' Wire





◀ **318821BB-669 PENDANT**

Burnished Bronze
 Finishes: BB, MN, PN
 Decorative White Fabric Shade

◀ **318821MN-669 PENDANT**

Matte Nickel
 Finishes: BB, MN, PN
 Decorative White Fabric Shade

◀ **318821PN-669 PENDANT**

Polished Nickel
 Finishes: BB, MN, PN
 Decorative White Fabric Shade

◀ **318821BB-670 PENDANT**

Burnished Bronze
 Finish: BB
 Decorative Tan Fabric Shade

8.75"W x 65"H • 65"H Overall
 Includes 6", 12" & 18"
 Removable Rods • Canopy:
 5.50"W x 2"H • 2 – 60 Watt E12
 Candelabra • Frosted Glass Diffuser
 with Finial • 1' Chain; 6' Wire



◀ **3913BB-453 CHANDELIER**

Burnished Bronze • Finishes: BB, MN, PN
 Decorative White Fabric Shade

▶ **3913BB-452 CHANDELIER**

Burnished Bronze • Finish: BB
 Decorative Tan Fabric Shade

20"W x 24"H • Canopy: 5"W x 1"H
 3 – 60 Watt E12 Candelabra
 10' Chain; 15' Wire



◀ **3913MN-453 CHANDELIER**

Matte Nickel • Finishes: BB, MN, PN
 Decorative White Fabric Shade

▶ **3913PN-453 CHANDELIER**

Polished Nickel • Finishes: BB, MN, PN
 Decorative White Fabric Shade

20"W x 24"H • Canopy: 5"W x 1"H
 3 – 60 Watt E12 Candelabra
 10' Chain; 15' Wire



▲ **3911BB-400 PENDANT** • *Burnished Bronze*
 24"W x 49.50"H • 49.50"H Overall Includes 6", 12"
 & 18"L Removable Rods • Canopy: 5.50"W x 1.75"H
 4 – 60 Watt E26 Medium • Decorative White Fabric
 Shade • Frosted Glass Diffuser with Finial • Finishes:
 BB, MN, PN • 1' Chain; 6' Wire



▲ **3911MN-400 PENDANT** • *Matte Nickel*
 24"W x 49.50"H • 49.50"H Overall Includes 6", 12"
 & 18"L Removable Rods • Canopy: 5.50"W x 1.75"H
 4 – 60 Watt E26 Medium • Decorative White Fabric
 Shade • Frosted Glass Diffuser with Finial • Finishes:
 BB, MN, PN • 1' Chain; 6' Wire



▲ **3911PN-400 PENDANT** • *Polished Nickel*
 24"W x 49.50"H • 49.50"H Overall Includes 6", 12"
 & 18"L Removable Rods • Canopy: 5.50"W x 1.75"H
 4 – 60 Watt E26 Medium • Decorative White Fabric
 Shade • Frosted Glass Diffuser with Finial • Finishes:
 BB, MN, PN • 1' Chain; 6' Wire



▲ **3911BB-401 PENDANT** • *Burnished Bronze*
 24"W x 49.50"H • 49.50"H Overall Includes 6", 12"
 & 18"L Removable Rods • Canopy: 5.50"W x 1.75"H
 4 – 60 Watt E26 Medium • Decorative Tan Fabric
 Shade • Frosted Glass Diffuser with Finial • Finish:
 BB • 1' Chain; 6' Wire



▲ **3910BB-457 PENDANT** · *Burnished Bronze*
 18"W x 49"H · 49"H Overall Includes 6", 12" & 18"L
 Removable Rods · Canopy: 5.50"W x 1.75"H
 3 – 60 Watt E26 Medium · Decorative White Fabric Shade
 Frosted Glass Diffuser with Finial · Finishes: BB, MN,
 PN · 1' Chain; 6' Wire



▲ **3910MN-457 PENDANT** · *Matte Nickel*
 18"W x 49"H · 49"H Overall Includes 6", 12" & 18"L
 Removable Rods · Canopy: 5.50"W x 1.75"H · 3 – 60
 Watt E26 Medium · Decorative White Fabric Shade
 Frosted Glass Diffuser with Finial · Finishes: BB,
 MN, PN · 1' Chain; 6' Wire



▲ **3910PN-457 PENDANT** · *Polished Nickel*
 18"W x 49"H · 49"H Overall Includes 6", 12" & 18"L
 Removable Rods · Canopy: 5.50"W x 1.75"H · 3 – 60
 Watt E26 Medium · Decorative White Fabric Shade
 Frosted Glass Diffuser with Finial · Finishes: BB,
 MN, PN · 1' Chain; 6' Wire



▲ **3910BB-456 PENDANT** · *Burnished Bronze*
 18"W x 49"H · 49"H Overall Includes 6", 12" & 18"L
 Removable Rods · Canopy: 5.50"W x 1.75"H · 3 – 60
 Watt E26 Medium · Decorative Tan Fabric Shade
 Frosted Glass Diffuser with Finial · Finish: BB
 1' Chain; 6' Wire



◀ **3914BB-459 CEILING**
Burnished Bronze

▶ **3914PN-459 CEILING**
Polished Nickel

17"W x 13"H · Canopy: 5.50"W x 1.75"H
 after Fixture Dimensions · 3 – 60 Watt
 E26 Medium · Decorative White Fabric
 Shade · Frosted Glass Diffuser with
 Finial · Finishes: BB, MN, PN
 Damp Rated



▼ **3914BB-458 CEILING** · *Burnished Bronze*
 17"W x 13"H · Canopy: 5.50"W x 2"H · 3 – 60 Watt E26
 Medium · Decorative Tan Fabric Shade · Frosted Glass
 Diffuser with Finial · Finish: BB · Damp Rated



▲ **3914MN-459 CEILING** · *Matte Nickel*
 17"W x 13"H · Canopy: 5.50"W x 2"H · 3 – 60 Watt E26
 Medium · Decorative White Fabric Shade · Frosted Glass
 Diffuser with Finial · Finishes: BB, MN, PN · Damp Rated



▲ **2015BB-480 CEILING** · *Burnished Bronze*
 15.75"W x 7.25"H · 3 – 40 Watt E26 Medium · Decorative
 White Fabric Shade · Frosted Glass Diffuser with Finial
 Finishes: BB, MN, PN · Damp Rated



▲ **2015PN-480 CEILING** · *Polished Nickel*
 15.75"W x 7.25"H · 3 – 40 Watt E26 Medium · Decorative
 White Fabric Shade · Frosted Glass Diffuser with Finial
 Finishes: BB, MN, PN · Damp Rated



▲ **2015BB-479 CEILING** · *Burnished Bronze*
 15.75"W x 7.25"H · 3 – 40 Watt E26 Medium · Decorative
 Tan Fabric Shade · Frosted Glass Diffuser with Finial
 Finish: BB · Damp Rated



▲ **2015MN-480 CEILING** · *Matte Nickel*
 15.75"W x 7.25"H · 3 – 40 Watt E26 Medium · Decorative
 White Fabric Shade · Frosted Glass Diffuser with Finial
 Finishes: BB, MN, PN · Damp Rated



▲ 9042BB-474 FOYER · *Burnished Bronze*
 ▲ 9042PN-474 FOYER · *Polished Nickel*

14"W x 28"H · Canopy: 5"W x 1"H · 2 – 60 Watt E26 Medium · Decorative White Fabric Shade · Frosted Glass Diffuser with Finial · Finishes: BB, MN, PN · 10' Chain; 15' Wire

▼ 9042BB-473 FOYER · *Burnished Bronze*

Finish: BB · Decorative Tan Fabric Shade

▼ 9042MN-474 FOYER · *Matte Nickel*

Finishes: BB, MN, PN · Decorative White Fabric Shade

14"W x 28"H · Canopy: 5"W x 1"H · 2 – 60 Watt E26 Medium Frosted Glass Diffuser with Finial · 10' Chain; 15' Wire



▲ 9047BB-478 FOYER · *Burnished Bronze*
 ▲ 9047PN-478 FOYER · *Polished Nickel*

11"W x 21.25"H · Canopy: 5"W x 1"H · 2 – 40 Watt E12 Candelabra · Decorative White Fabric Shade Frosted Glass Diffuser with Finial · Finishes: BB, MN, PN · 10' Chain; 15' Wire

▼ 9047BB-477 FOYER · *Burnished Bronze*

Finish: BB · Decorative Tan Fabric Shade

▼ 9047MN-478 FOYER · *Matte Nickel*

Finishes: BB, MN, PN · Decorative White Fabric Shade

11"W x 21.25"H · Canopy: 5"W x 1"H · 2 – 40 Watt E12 Candelabra · Frosted Glass Diffuser with Finial · 10' Chain; 15' Wire



▼ **9041BB-471 FOYER** · *Burnished Bronze*

Finish: BB · Decorative Tan Fabric Shade

▼ **9041PN-472 FOYER** · *Polished Nickel*

Finishes: BB, MN, PN · Decorative White Fabric Shade

14"W x 28"H · Canopy: 5"W x 1"H · 2 – 60 Watt E26 Medium
Frosted Glass Diffuser with Finial · 10' Chain; 15' Wire



▲ **9041BB-472 FOYER** · *Burnished Bronze*

▲ **9041MN-472 FOYER** · *Matte Nickel*

14"W x 28"H · Canopy: 5"W x 1"H · 2 – 60 Watt E26
Medium · Decorative White Fabric Shade · Frosted Glass
Diffuser with Finial · Finishes: BB, MN, PN · 10' Chain;
15' Wire

▼ **9046BB-462 FOYER** · *Burnished Bronze*

Finish: BB · Decorative Tan Fabric Shade

▼ **9046PN-463 FOYER** · *Polished Nickel*

Finishes: BB, MN, PN · Decorative White Fabric Shade

11"W x 21.25"H · Canopy: 5"W x 1"H · 2 – 40 Watt E12
Candelabra · Frosted Glass Diffuser with Finial · 10' Chain;
15' Wire



▲ **9046BB-463 FOYER** · *Burnished Bronze*

▲ **9046MN-463 FOYER** · *Matte Nickel*

11"W x 21.25"H · Canopy: 5"W x 1"H · 2 – 40 Watt
E12 Candelabra · Decorative White Fabric Shade
Frosted Glass Diffuser with Finial · Finishes: BB,
MN, PN · 10' Chain; 15' Wire

▶ **1232BB-451 SCONCE** · *Burnished Bronze*

15"W x 17"H x 7"E · Backplate: 5.75"W x 5.75"H x 1"E
 Ctr/Top: 14" Ctr/Btm: 3" · 2 – 60 Watt E12 Candelabra
 Decorative White Fabric Stay-Straight Shades · Finishes:
 BB, MN, PN · Damp Rated

▶ **1231BB-451 SCONCE** · *Burnished Bronze*

6"W x 15.75"H x 7"E · Backplate: 5.75"W x 5.75"H x 1"E
 Ctr/Top: 13" Ctr/Btm: 3" · 1 – 60 Watt E12 Candelabra
 Decorative White Fabric Stay-Straight Shade · Finishes:
 BB, MN, PN · Damp Rated



◀ **1237BB-451 VANITY** · *Burnished Bronze*

17.50"W x 13.50"H x 7.50"E · Backplate: 5.75"W x 5.75"H x 1"E
 Ctr/Top: 10.75" Ctr/Btm: 2.75" · 2 – 60 Watt E12 Candelabra
 Decorative White Fabric Stay-Straight Shades · Finishes: BB,
 MN, PN · Damp Rated



▶ **1238BB-451 VANITY** · *Burnished Bronze*

25.50"W x 13.50"H x 7.50"E
 Backplate: 5.75"W x 5.75"H x 1"E · Ctr/Top: 10.75"
 Ctr/Btm: 2.75" · 3 – 60 Watt E12 Candelabra
 Decorative White Fabric Stay-Straight Shades
 Finishes: BB, MN, PN · Damp Rated



▲ **1239BB-451 VANITY** · *Burnished Bronze*

35"W x 13.50"H x 7.50"E · Backplate: 5.75"W x 5.75"H x 1"E · Ctr/Top:
 10.75" Ctr/Btm: 2.75" · 4 – 60 Watt E12 Candelabra · Decorative White
 Fabric · Stay-Straight Shades · Finishes: BB, MN, PN · Damp Rated



◀ **1232BB-450 SCONCE** • *Burnished Bronze*

15"W x 17"H x 7"E • Backplate: 5.75"W x 5.75"H x 1"E
Ctr/Top: 14" Ctr/Btm: 3" • 2 – 60 Watt E12 Candelabra
Decorative Tan Fabric Stay-Straight Shades • Finish: BB
Damp Rated

◀ **1231BB-450 SCONCE** • *Burnished Bronze*

6"W x 15.75"H x 7"E • Backplate: 5.75"W x 5.75"H x 1"E
Ctr/Top: 13" Ctr/Btm: 3" • 1 – 60 Watt E12 Candelabra
Decorative Tan Fabric Stay-Straight Shade • Finish: BB
Damp Rated



S450 SHADE

5.75"W x 5"H
Stay-Straight

▶ **1237BB-450 VANITY** • *Burnished Bronze*

17.50"W x 13.50"H x 7.50"E • 5.75"W x 5.75"H x 1"E
Ctr/Top: 10.75" Ctr/Btm: 2.75" • 2 – 60 Watt E12 Candelabra
Decorative Tan Fabric Stay-Straight Shades • Finish: BB
Damp Rated



◀ **1238BB-450 VANITY** • *Burnished Bronze*

25.50"W x 13.50"H x 7.50"E • Backplate:
5.75"W x 5.75"H x 1"E • Ctr/Top: 10.75"
Ctr/Btm: 2.75" • 3 – 60 Watt E12 Candelabra
Decorative Tan Fabric Stay-Straight Shades
Finish: BB • Damp Rated



▲ **1239BB-450 VANITY** • *Burnished Bronze*

35"W x 13.50"H x 7.50"E • Backplate: 5.75"W x 5.75"H x 1"E • Ctr/Top:
10.75" Ctr/Btm: 2.75" • 4 – 60 Watt E12 Candelabra • Decorative Tan
Fabric Stay-Straight Shades • Finish: BB • Damp Rated

► **1232MN-451 SCONCE** · *Matte Nickel*
 15"W x 17"H x 7"E · Backplate: 5.75"W x 5.75"H x 1"E
 Ctr/Top: 14" Ctr/Btm: 3" · 2 – 60 Watt E12 Candelabra
 Decorative White Fabric Stay-Straight Shades · Finishes:
 BB, MN, PN · Damp Rated



► **1231MN-451 SCONCE** · *Matte Nickel*
 6"W x 15.75"H x 7"E · Backplate: 5.75"W x 5.75"H x 1"E
 Ctr/Top: 13" Ctr/Btm: 3" · 1 – 60 Watt E12 Candelabra
 Decorative White Fabric Stay-Straight Shade · Finishes:
 BB, MN, PN · Damp Rated



S451 SHADE
 5.75"W x 5"H
 Stay-Straight



◀ **1237MN-451 VANITY** · *Matte Nickel*
 17.50"W x 13.50"H x 7.50"E · Backplate: 5.75"W x 5.75"H x 1"E
 Ctr/Top: 10.75" Ctr/Btm: 2.75" · 2 – 60 Watt E12 Candelabra
 Decorative White Fabric Stay-Straight Shades · Finishes: BB,
 MN, PN · Damp Rated



► **1238MN-451 VANITY** · *Matte Nickel*
 25.50"W x 13.50"H x 7.50"E · Backplate:
 5.75"W x 5.75"H x 1"E · Ctr/Top: 10.75" Ctr/Btm: 2.75"
 3 – 60 Watt E12 Candelabra · Decorative White Fabric
 Stay-Straight Shades · Finishes: BB, MN, PN · Damp Rated



▲ **1239MN-451 VANITY** · *Matte Nickel*
 35"W x 13.50"H x 7.50"E · Backplate: 5.75"W x 5.75"H x 1"E · Ctr/Top:
 10.75" Ctr/Btm: 2.75" · 4 – 60 Watt E12 Candelabra · Decorative White
 Fabric Stay-Straight Shades · Finishes: BB, MN, PN · Damp Rated



◀ **1232PN-451 SCONCE** · *Polished Nickel*
 15"W x 17"H x 7"E · Backplate: 5.75"W x 5.75"H x 1"E
 Ctr/Top: 14" Ctr/Btm: 3" · 2 – 60 Watt E12 Candelabra
 Decorative White Fabric Stay-Straight Shades · Finishes:
 BB, MN, PN · Damp Rated



◀ **1231PN-451 SCONCE** · *Polished Nickel*
 6"W x 15.75"H x 7"E · Backplate: 5.75"W x 5.75"H x 1"E
 Ctr/Top: 13" Ctr/Btm: 3" · 1 – 60 Watt E12 Candelabra
 Decorative White Fabric Stay-Straight Shade · Finishes:
 BB, MN, PN · Damp Rated

▶ **1237PN-451 VANITY** · *Polished Nickel*
 17.50"W x 13.50"H x 7.50"E · Backplate: 5.75"W x 5.75"H x 1"E
 Ctr/Top: 10.75" Ctr/Btm: 2.75" · 2 – 60 Watt E12 Candelabra
 Decorative White Fabric Stay-Straight Shades · Finishes: BB,
 MN, PN · Damp Rated



◀ **1238PN-451 VANITY** · *Polished Nickel*
 25.50"W x 13.50"H x 7.50"E · Backplate:
 5.75"W x 5.75"H x 1"E · Ctr/Top: 10.75" Ctr/Btm: 2.75"
 3 – 60 Watt E12 Candelabra · Decorative White Fabric
 Stay-Straight Shades · Finishes: BB, MN, PN · Damp Rated



▲ **1239PN-451 VANITY** · *Polished Nickel*
 35"W x 13.50"H x 7.50"E · Backplate: 5.75"W x 5.75"H x 1"E · Ctr/Top:
 10.75" Ctr/Btm: 2.75" · 4 – 60 Watt E12 Candelabra · Decorative White
 Fabric Stay-Straight Shades · Finishes: BB, MN, PN · Damp Rated



milan
collection

IN CAPITAL GOLD



◀ **419781CG CHANDELIER** • *Capital Gold*
33"W x 38.50"H • Canopy: 5"W x .75"H • 8 – 60 Watt
E12 Candelabra • Finish: CG • Includes K9 Crystals and
K9 Crystal Column • 10' Chain; 15' Wire

▶ **419741CG CHANDELIER** • *Capital Gold*
28.50"W x 26.50"H • Canopy: 5"W x .75"H • 4 – 60 Watt
E12 Candelabra • Finish: CG • Includes K9 Crystals and
K9 Crystal Column • 10' Chain; 15' Wire



CG-Capital Gold





◀ **319741CG-675 PENDANT** • *Capital Gold*
15"W x 13"H • Canopy: 5"W x .75"H • 4 – 60 Watt E12
Candelabra • Decorative White Fabric Shade • Frosted
Glass Diffuser • Finish: CG • Includes K9 Crystals
10' Chain; 15' Wire



▲ **619711CG SCONCE** • *Capital Gold*
4.75"W x 14"H x 5"E • Backplate: 4.75"W x 12"H x 1.75"E
Ctr/Top: 8" Ctr/Btm: 6" • 1 – 60 Watt E12 Candelabra
Finish: CG • Includes K9 Crystals • Damp Rated



◀ **519741CG FOYER** • *Capital Gold*
15"W x 30.50"H • Canopy: 5"W x .75"H • 4 – 60 Watt
E12 Candelabra • Finish: CG • Includes K9 Crystals
10' Chain; 15' Wire

Coordinates With

ABELLA
123031CG-436 VANITY
see page 15



BLAKELY
9482CG FOYER
see page 81



2325CG CEILING
see page 456



▲ **319742CG-676 PENDANT** • *Capital Gold*
24"W x 17.25"H • Canopy: 5"W x .75"H • 6 – 60 Watt
E12 Candelabra • Decorative White Fabric Shade
Finish: CG • Includes K9 Crystals • 10' Chain; 15' Wire



morgan
collection

IN BURNISHED BRONZE
& POLISHED NICKEL



◀ **4818PN CHANDELIER** • *Polished Nickel*
32.50"W x 31.50"H • Canopy: 5"W x .75"H • 8 – 60 Watt
E12 Candelabra • Finishes: BB, PN • K9 Crystals
10' Chain; 15' Wire

▶ **4818BB CHANDELIER** • *Burnished Bronze*
32.50"W x 31.50"H • Canopy: 5"W x .75"H • 8 – 60 Watt
E12 Candelabra • Finishes: BB, PN • K9 Crystals
10' Chain; 15' Wire





◀ **4817PN CHANDELIER** · *Polished Nickel*

▼ **4817BB CHANDELIER** · *Burnished Bronze*

24.25"W x 21.75"H · Canopy: 5"W x .75"H · 8 – 60 Watt
E12 Candelabra · Finishes: BB, PN · K9 Crystals
10' Chain; 15' Wire



▲ **7004PN ISLAND** · *Polished Nickel*

▶ **7004BB ISLAND** · *Burnished Bronze*

40"W x 71"H x 12"E · 71"H Overall Includes 6", 12" &
18"L Removable Rods · Canopy: 22.25"L x 5"W x .75"H
8 – 60 Watt E12 Candelabra · Finishes: BB, PN
K9 Crystals · 1' Chain; 6' Wire



- ◀ **4811PN SCONCE** · *Polished Nickel*
- ◀ **4811BB SCONCE** · *Burnished Bronze*



5.25"W x 16"H x 3.75"E
 Mirror Backplate: 5.25"W x 16"H x .75"E
 Ctr/Top: 8" Ctr/Btm: 8" · 1 – 60 Watt E12
 Candelabra · Finishes: BB, PN · K9 Crystal
 Damp Rated
ADA

7001BB FOYER
7001PN FOYER
 Includes Flush
 Mount Option
 12"W x 21.75"H



- ▲ **7001PN FOYER** · *Polished Nickel*
- ▲ **7001BB FOYER** · *Burnished Bronze*

12"W x 22.75"H · Canopy: 5"W x .75"H
 4 – 60 Watt E12 Candelabra · Finishes: BB,
 PN · K9 Crystals · 10' Chain; 15' Wire



- ◀ **7002PN FOYER** · *Polished Nickel*
- ◀ **7002BB FOYER** · *Burnished Bronze*

15"W x 26.75"H · Canopy: 5"W x .75"H
 4 – 60 Watt E12 Candelabra · Finishes: BB,
 PN · K9 Crystals · 10' Chain; 15' Wire



- ◀ **7003PN FOYER** · *Polished Nickel*
- ▶ **7003BB FOYER** · *Burnished Bronze*

22"W x 38"H · Canopy: 5"W x .75"H
 8 – 60 Watt E12 Candelabra
 Finishes: BB, PN · K9 Crystals
 10' Chain; 15' Wire





nash
collection

IN GUNMETAL



◀ **413261GM CHANDELIER** · *Gunmetal*
29"W x 26.50"H · Canopy: 5"W x .75"H · 6 – 75 Watt
E26 Medium · Finish: GM · 10' Chain; 15' Wire



▲ **613221GM-360 SCONCE** · *Gunmetal*
5"W x 16"H x 6.50"E · Backplate:
5"W x 5"H x 1.25"E · Ctr/Top: 8" Ctr/Btm: 8"
2 – 75 Watt E26 Medium · Soft White Glass
Finish: GM · Damp Rated



◀ **613211GM SCONCE** · *Gunmetal*
9.75"W x 15.25"H x 5.50"E
Backplate: 7"W x 13.75"H x .75"E · Ctr/Top: 8.25"
Ctr/Btm: 7" · 1 – 75 Watt E26 Medium · Soft White
Glass · Finish: GM · Damp Rated



▲ **213211GM-LD CEILING** · *Gunmetal*
16"W x 4.50"H · Lumens: 2125 · CRI > 80
Volts/Wattage: 120V 50/60 HZ/25W · Color Temp:
3000K · Milk Glass · Finish: GM · Damp Rated · [LED]

Dimmable – LED Dimmer Recommended



▲ **413201GM CHANDELIER** · *Gunmetal*
37.50"W x 38"H · Canopy: 5"W x .75"H · 14 – 75 Watt
E26 Medium · Finish: GM · 10' Chain; 15' Wire

50+LBS

Additional mounting support required



GM-Gunmetal

► **412661WG-654 CHANDELIER** · *Winter Gold*

Shown with Shades

28"W x 27"H · Canopy: 5"W x 1"H · 6 – 60 Watt

E12 Candelabra · Decorative White Fabric Stay-Straight

Shades · Finish: WG · 10' Chain; 15' Wire



noelle
collection

IN WINTER GOLD



◀ Remove the shades from 412661WG-654 to take this chandelier from Traditional to Transitional. Note: When you remove the shades the fixture width is 26.50"W.

SH654 SHADE
 6"W x 4.75"H
 Stay-Straight
 Shade



▲ **412601WG-654 CHANDELIER** · *Winter Gold*
 37"W x 44.25"H · Canopy: 5"W x 1"H · 10 – 60 Watt
 E12 Candelabra · Decorative White Fabric Stay-Straight
 Shades · Finish: WG · 10' Chain; 15' Wire

Coordinates With

CAMILLE
210731SF CEILING
 see page 99



WESTBROOK
61011WG SCONCE
 see page 328



OLIVIA
115031WG-375 VANITY
 see page 257



MERCER
321243WG-CR PENDANT
 see page 218



WG-Winter Gold



nora

collection

IN FRENCH COUNTRY



◀ **410301FC CHANDELIER** · *French Country*
 36"W x 42"H · Canopy: 5"W x 1"H · 10 – 60 Watt
 E12 Candelabra · Finish: FC · 10' Chain; 15' Wire



◀ **610311FC SCONCE**
French Country
 5"W x 17.50"H x 9"E
 Backplate: 5"W x 13.50"H x 1"E
 Ctr/Top: 10.75" Ctr/Btm: 6.75"
 1 – 60 Watt E12 Candelabra
 Finish: FC · Damp Rated



▶ **410361FC CHANDELIER** · *French Country*
 28"W x 32"H · Canopy: 5"W x 1"H · 6 – 60 Watt
 E12 Candelabra · Finish: FC · 10' Chain; 15' Wire



FC-French Country



◀ **3798BB PENDANT** • *Burnished Bronze*
15"W x 10"H • Canopy: 5"W x .75"H • 1 – 100 Watt
E26 Medium • Finish: BB • 10' Chain; 15' Wire
Damp Rated

o'neal
collection

IN BURNISHED BRONZE

▶ **3797BB PENDANT** • *Burnished Bronze*
9.50"W x 9"H • Canopy: 5"W x .75"H • 1 – 100 Watt E26
Medium • Finish: BB • 10' Chain; 15' Wire • Damp Rated





◀ **3791BB SCONCE** • *Burnished Bronze*
 9.50"W x 7.75"H x 10.50"E • Backplate: 5"W x 5"H x .75"E
 Ctr/Top: 3.50" Ctr/Btm: 4.25" • 1 – 100 Watt E26 Medium
 Finish: BB • Damp Rated



▶ **3792BB VANITY** • *Burnished Bronze*
 19.75"W x 7.75"H x 10.50"E
 Backplate: 5"W x 5"H x .75"E
 Ctr/Top: 3.50" Ctr/Btm: 4.25" • 2 – 100 Watt
 E26 Medium • Finish: BB • Damp Rated



▲ **3793BB VANITY** • *Burnished Bronze*
 30"W x 7.75"H x 10.50"E • Backplate: 5"W x 5"H x .75"E
 Ctr/Top: 3.50" Ctr/Btm: 4.25" • 3 – 100 Watt E26
 Medium • Finish: BB • Damp Rated



olivia
collection

IN WINTER GOLD



◀ **415002WG CHANDELIER** · *Winter Gold*
58"W x 63"H · Canopy: 7"W x 1.50"H · 16 – 60 Watt
E12 Candelabra · Finish: WG · K9 Crystals
10' Chain; 15' Wire
50+LBS
Additional mounting support required

▶ **415061WG CHANDELIER** · *Winter Gold*
28.25"W x 31.75"H · Canopy: 5"W x 1"H · 6 – 60 Watt
E12 Candelabra · Finish: WG · K9 Crystals · 10' Chain;
15' Wire



WG-Winter Gold



◀ **415001WG CHANDELIER** • *Winter Gold*
35.25"W x 39.75"H • Canopy: 5"W x 1"H • 10 – 60 Watt
E12 Candelabra • Finish: WG • K9 Crystals • 10' Chain;
15' Wire



▲ **515042WG FOYER** • *Winter Gold*
14.50"W x 26.50"H • Canopy: 5"W x 1"H • 4 – 60 Watt
E12 Candelabra • Finish: WG • K9 Crystals • 10' Chain;
15' Wire

◀ **515041WG FOYER** • *Winter Gold*
15"W x 28.25"H • Canopy: 5"W x 1"H • 4 – 60 Watt
E12 Candelabra • Finish: WG • K9 Crystals • 10' Chain;
15' Wire




◀ **615011WG-671 SCONCE** · *Winter Gold*
 6"W x 14.75"H x 6.50"E · Backplate: 6"W x 6"H x 1"E
 Ctr/Top: 9" Ctr/Btm: 5.75" · 1 – 60 Watt E12 Candelabra
 Decorative White Fabric Stay-Straight Shade · Finish: WG
 K9 Crystals · Damp Rated



▲ **115041WG-375 VANITY** · *Winter Gold*
 32.50"W x 10.50"H x 6.25"E · Backplate: 6"W x 6"H x 1"E
 Ctr/Top: 2.75" Ctr/Btm: 5.75" · 4 – 100 Watt E26
 Medium · Soft White Glass · Finish: WG · K9 Crystals
 Damp Rated



▶ **115031WG-375 VANITY** · *Winter Gold*
 23.75"W x 10.50"H x 6.25"E · Backplate: 6"W x 6"H x 1"E
 Ctr/Top: 2.75" Ctr/Btm: 5.75" · 3 – 100 Watt E26
 Medium · Soft White Glass · Finish: WG · K9 Crystals
 Damp Rated



◀ **115021WG-375 VANITY** · *Winter Gold*
 17"W x 10.50"H x 6.25"E · Backplate: 6"W x 6"H x 1"E
 Ctr/Top: 2.75" Ctr/Btm: 5.75" · 2 – 100 Watt E26
 Medium · Soft White Glass · Finish: WG · K9 Crystals
 Damp Rated





oxford
collection

IN SILVER PATINA



◀ **419601SP CHANDELIER** • *Silver Patina*

34.25"W x 36"H • Canopy: 5"W x .75"H • 12 – 60 Watt
E12 Candelabra • Finish: SP • 10' Chain; 15' Wire

▶ **619611SP-419 SCONCE** • *Silver Patina*

5"W x 16"H x 5.5"E • Backplate: 5"W x 9"H x 1"E
Ctr/Top: 8" Ctr/Btm: 8" • 1 – 60 Watt E12 Candelabra
Clear Swirl Glass • Finish: SP • Damp Rated



▶ **519641SP FOYER** • *Silver Patina*

16"W x 26.50"H • Canopy: 5"W x .75"H • 4 – 60 Watt
E12 Candelabra • Finish: SP • 10' Chain; 15' Wire



GL419
3.25"W x 5.25"H

▼ **419681SP CHANDELIER** • *Silver Patina*

28.5"W x 29"H • Canopy: 5"W x .75"H • 8 – 60 Watt
E12 Candelabra • Finish: SP • 10' Chain; 15' Wire



▲ **119631SP-419 VANITY** • *Silver Patina*

22"W x 9.25"H x 6.50"E • Backplate: 8.25"W x 5"H x 1"E
Ctr/Top: 7" Ctr/Btm: 2.25" • 3 – 60 Watt E12 Candelabra
Clear Swirl Glass • Finish: SP • Damp Rated



SP-Silver Patina





pearson
collection

IN BLACK IRON




◀ **4912BI-000 CHANDELIER** • *Black Iron*
 48.25"W x 41.50"H • Canopy: 5"W x .75"H • 12 – 60 Watt
 E12 Candelabra • Finish: BI • 10' Chain; 15' Wire



▲ **4911BI SCONCE** • *Black Iron*
 8.25"W x 11.75"H x 3.25"E
 Backplate: 4.5"W x 11"H x .75"E
 Ctr/Top: 6" Ctr/Btm: 5.75" • 1 – 60 Watt
 E12 Candelabra • Finish: BI • Damp Rated
ADA



◀ **4916BI-000 CHANDELIER** • *Black Iron*
 26"W x 30.50"H • Canopy: 5"W x .75"H • 6 – 60 Watt
 E12 Candelabra • Finish: BI • 10' Chain; 15' Wire



▲ **4910BI CHANDELIER** • *Black Iron*
 48"W x 43"H • Canopy: 5"W x .75"H • 24 – 60 Watt
 E12 Candelabra • Finish: BI • 10' Chain; 15' Wire



◀ **4918BI-000 CHANDELIER** • *Black Iron*
 36"W x 33"H • Canopy: 5"W x .75"H • 8 – 60 Watt
 E12 Candelabra • Finish: BI • 10' Chain; 15' Wire



perry
collection

IN BRONZE AND OAK
& POLISHED NICKEL

perry | IN BRONZE AND OAK & POLISHED NICKEL



◀ **4866BA PENDANT** · *Bronze and Oak*
 ▼ **4866PN PENDANT** · *Polished Nickel* · Includes K9 Crystal
 23"W x 28.50"H · Canopy: 5"W x .75"H · 6 – 60 Watt
 E12 Candelabra · Finish: BA, PN · 10' Chain; 15' Wire



◀ **4864BA PENDANT** · *Bronze and Oak*
 ▼ **4864PN PENDANT** · *Polished Nickel* · Includes K9 Crystal
 13"W x 18"H · Canopy: 5"W x .75"H · 4 – 60 Watt
 E12 Candelabra · Finish: BA, PN · 10' Chain; 15' Wire

Coordinates With



HUDSON
611911PN
SCONCE
 see page 185



MIDTOWN
1231BB-451
SCONCE
 see page 234



porter
collection

IN RENAISSANCE BROWN



▲ **420961RB-425 CHANDELIER** • *Renaissance Brown*
 28.50"W x 28.25"H • Canopy: 5"W x .75"H • 6 – 100 Watt
 E26 Medium • Clear Water Glass • Finish: RB
 10' Chain; 15' Wire



GL425 GLASS
 4.25"W x 5.50"H

▶ **520941RB FOYER** • *Renaissance Brown*
 16"W x 28"H • Canopy: 5"W x .75"H • 4 – 60 Watt
 E12 Candelabra • Finish: RB • 10' Chain; 15' Wire



RB-Renaissance Brown

Coordinates
 With

4500SY FOYER
 see page 439



**MIDTOWN
 3914BB-459 CEILING**
 see page 230



**MIDTOWN
 2015BB-480 CEILING**
 see page 231





▲ **120941RB-425 VANITY** · Renaissance Brown
33.50"W x 9"H x 6.75"E · Backplate: 5"W x 5"H x 1"E
Ctr/Top: 2.50" Ctr/Btm: 6.50" · 4 – 100 Watt E26
Medium · Clear Water Glass · Finish: RB · Damp Rated



▲ **120931RB-425 VANITY** · Renaissance Brown
24"W x 9"H x 6.75"E · Backplate: 5"W x 5"H x 1"E
Ctr/Top: 2.50" Ctr/Btm: 6.50" · 3 – 100 Watt E26
Medium · Clear Water Glass · Finish: RB · Damp Rated



◀ **120921RB-425 VANITY** · Renaissance Brown
14.25"W x 9"H x 6.75"E · Backplate: 5"W x 5"H x 1"E
Ctr/Top: 6.50" Ctr/Btm: 2.50" · 2 – 100 Watt E26
Medium · Clear Water Glass · Finish: RB · Damp Rated



◀ **420901RB-425 CHANDELIER** • *Renaissance Brown*
35"W x 40"H • Canopy: 5"W x .75"H • 10 – 100 Watt
E26 Medium • Clear Water Glass • Finish: RB
10' Chain; 15' Wire



▶ **620911RB-425 SCONCE** • *Renaissance Brown*
5"W x 24"H x 6.25"E • Backplate: 4.50"W x 7.50"H x 1"E
Ctr/Top: 9.75" Ctr/Btm: 14.25" • 1 – 100 Watt E26
Medium • Clear Water Glass • Finish: RB • Damp Rated



ravenwood
collection

IN BLACK IRON



Coordinates
With

**PENDANT
312541BI**
see page 461



**AXIS
4236AB PENDANT**
see page 47



**PEARSON
4911BI SCIONCE**
see page 261



▲ **419801BI CHANDELIER** • *Black Iron*
38.50"W x 45"H • Canopy: 5"W x .75"H • 16 – 60 Watt
E12 Candelabra • Finish: BI • 10' Chain; 15' Wire



BI-Black Iron



◀ **519841BI FOYER** • *Black Iron*
16.25"W x 26"H • Canopy: 5"W x .75"H • 4 – 60 Watt
E12 Candelabra • Finish: BI • 10' Chain; 15' Wire



◀ **619821BI SCONCE** • *Black Iron*
9.75"W x 22"H x 4"E • Backplate: 4.75"W x 10.50"H x 1"E
Ctr/Top: 9.25" Ctr/Btm: 12.75" • 2 – 60 Watt E12 Candelabra
Finish: BI • Damp Rated • **ADA**



▶ **419881BI CHANDELIER** • *Black Iron*
31.50"W x 29.75"H • Canopy: 5"W x .75"H
8 – 60 Watt E12 Candelabra • Finish: BI
10' Chain; 15' Wire



◀ **119821BI-435 VANITY** • *Black Iron*

13.25"W x 9.50"H x 5.50"E

Backplate: 8.50"W x 5"H x .75"E • Ctr/Top: 2.50"

Ctr/Btm: 7" • 2 – 100 Watt E26 Medium • Clear

Seeded Glass • Finish: BI • Damp Rated



GL435 GLASS

4"W x 6.75"H

▼ **119831BI-435 VANITY** • *Black Iron*

23"W x 9.50"H x 5.50"E

Backplate: 8.50"W x 5"H x .75"E • Ctr/Top: 7"

Ctr/Btm: 2.50" • 3 – 100 Watt E26 Medium • Clear

Seeded Glass • Finish: BI • Damp Rated



▲ **119841BI-435 VANITY** • *Black Iron*

32.75"W x 9.50"H x 5.50"E • Backplate: 8.50"W x 5"H x .75"E

Ctr/Top: 2.50" Ctr/Btm: 7" • 4 – 100 Watt E26 Medium

Clear Seeded Glass • Finish: BI • Damp Rated



regan
collection

IN CAPITAL GOLD



► **419402CG-417 CHANDELIER** · *Capital Gold*
60.25"W x 93"H · 93"H Overall Includes 6", 12" &
18"L Removable Rods · Canopy: 5"W x .75"H
18 – 60 Watt E26 Medium · Clear Seeded Glass
Finish: CG · 1' Chain; 6' Wire

GL417 GLASS
2.75"W x 9"H



CG-Capital Gold

**DONNY
OSMOND** home™
BY DONNY & DEBBIE OSMOND



◀ **419461CG-417 CHANDELIER** • *Capital Gold*
26"W x 67.25"H • 67.25"H Overall Includes 6", 12" &
18"L Removable Rods • Canopy: 5"W x.75"H • 6 – 60
Watt E26 Medium • Clear Seeded Glass • Finish: CG
1' Chain; 6' Wire

▼ **519441CG FOYER** • *Capital Gold*
12"W x 15.50"H • Canopy: 5"W x.75"H
4 – 60 Watt E12 Candelabra • Finish: CG
10' Chain; 15' Wire



▲ **519442CG-417 FOYER** • *Capital Gold*
15"W x 28"H • Canopy: 5"W x .75"H • 4 – 60 Watt
E26 Medium • Clear Seeded Glass • Finish: CG
10' Chain; 15' Wire

Coordinates With

2325CG CEILING
see page 415



**FIRE AND ICE
420861FI CHANDELIER**
see page 171



**FIRE AND ICE
620811FI SCONCE**
see page 170



▲ **419401CG-417 CHANDELIER** • *Capital Gold*
33"W x 77.25"H • 77.25"H Overall Includes 6", 12" &
18"L Removable Rods • Canopy: 5"W x .75"H • 10 – 60
Watt E26 Medium • Clear Seeded Glass • Finish: CG
1' Chain; 6' Wire

**DONNY
OSMOND** home™
BY DONNY & DEBBIE OSMOND



◀ **219441CG FOYER** · *Capital Gold*
15"W x 13.25"H · Canopy: 5"W x .75"H · 4 – 60 Watt
E12 Candelabra · Finish: CG · 10' Chain; 15' Wire

**219441CG
CEILING**
15"W x 10.75"H
Includes Flush
Mount Option



◀ **619411CG-417 SCONCE** · *Capital Gold*
7"W x 24"H x 5.75"E · Backplate: 5"W x 5"H x .75"E
Ctr/Top: 10" Ctr/Btm: 14" · 1 – 60 Watt E26 Medium
Clear Seeded Glass · Finish: CG · Damp Rated

▶ **319411CG-437-LD PENDANT** · *Capital Gold*
6.50"W x 64.25"H Overall Includes 6", 12" & 18"L
Removable Rods · Canopy: 5"W x .75"H · Lumens: 780,
CRI >90, Volts/Watts: 120V/14W, Color Temperature:
3000K · Clear Seeded Glass · Finish: CG · 1' Chain;
6' Wire · [LED]



► **119421CG-418-LD VANITY** · *Capital Gold*
 14"W x 7.50"H x 7"E · Backplate: 5"W x 5"H x .75"E
 Ctr/Top: 2.50" Ctr/Btm: 5" · Lumens: 630, CRI >90,
 Volts/Watts:120V/8W, Color Temperature: 3000K
 Clear Seeded Glass · Finish: CG · Damp Rated · [LED]



▲ **119431CG-418-LD VANITY** · *Capital Gold*
 23.50"W x 7.50"H x 7"E · Backplate: 5"W x 5"H x .75"E
 Ctr/Top: 2.50" Ctr/Btm: 5" · Lumens: 945, CRI >90,
 Volts/Watts: 120V/12W, Color Temperature: 3000K
 Clear Seeded Glass · Finish: CG · Damp Rated · [LED]



▲ **119441CG-418-LD VANITY** · *Capital Gold*
 33"W x 7.50"H x 7"E · Backplate: 5"W x 5"H x .75"E
 Ctr/Top: 2.50 Ctr/Btm: 5" · Lumens: 1260, CRI > 90,
 Volts/Watts: 120V/16W, Color Temperature: 3000K
 Clear Seeded Glass · Finish: CG · Damp Rated · [LED]



◀ **312042RT PENDANT** · *Rustic*
18"W x 15.75"H · Canopy: 5"W x .75"H · 4 – 60 Watt
E12 Candelabra · Ribbed Glass · Finish: RT · 10' Chain;
15' Wire

reid
collection
IN RUSTIC



**212041RT
CEILING**
Includes
Pendant Option
14.25"W x 19.25"H

▶ **212041RT CEILING** · *Rustic*
14.25"W x 19"H · Canopy: 5"W x .75"H · 4 – 60 Watt
E12 Candelabra · Ribbed Glass · Finish: RT
10' Chain; 15' Wire



◀ **212031RT CEILING** · *Rustic*
14.25"W x 7.25"H · 3 – 60 Watt E26 Medium
Ribbed Glass · Frosted Glass Diffuser with Finial
Finish: RT · Damp Rated

▶ **412001RT-323 CHANDELIER** · *Rustic*
34.50"W x 34"H · Canopy: 5"W x .75"H
10 – 60 Watt E26 Medium · Soft White Glass
Finish: RT · 10' Chain; 15' Wire



RT-Rustic



GL323 GLASS
5"W x 6"H

▶ **612011RT SCONCE** • *Rustic*
7"W x 18"H x 4.75"E • Backplate: 7"W x 18"H x .75"E
Ctr/Top: 9" Ctr/Btm: 9" • 1 – 100 Watt E26 Medium
Ribbed Glass • Finish: RT • Damp Rated



▲ **412061RT-323 CHANDELIER** • *Rustic*
29"W x 26.50"H • Canopy: 5"W x .75"H • 6 – 100 Watt
E26 Medium • Soft White Glass • Finish: RT
10' Chain; 15' Wire



▲ **112041RT-323 VANITY** · *Rustic*
 23.75"W x 8.25"H x 10.50"E · Backplate: 9.5"W x 4.5"H x .75"E
 Ctr/Top: 2.75" Ctr/Btm: 5.50" · 4 – 100 Watt E26 Medium
 Soft White Glass · Finish: RT · Damp Rated



▲ **112031RT-323 VANITY** · *Rustic*
 23.75"W x 8.25"H x 7.50"E · Backplate: 9.5"W x 4.5"H x .75"E
 Ctr/Top: 5.50" Ctr/Btm: 2.75" · 3 – 100 Watt E26 Medium
 Soft White Glass · Finish: RT · Damp Rated

▶ **112021RT-323 VANITY** · *Rustic*
 17.50"W x 8.25"H x 7.50"E
 Backplate: 9.5"W x 4.5"H x .75"E · Ctr/Top: 2.75"
 Ctr/Btm: 5.50" · 2 – 100 Watt E26 Medium · Soft White
 Glass · Finish: RT · Damp Rated





renaissance
collection

IN RENAISSANCE
& RENAISSANCE BROWN



◀ **421502RN CHANDELIER** · Renaissance
57"W x 66"H · Canopy: 7"W x 1.50"H · 18 – 60 Watt E12
Candelabra · Finish: RN · 10' Chain; 15' Wire
50+LBS
Additional mounting support required



▶ **621511RN SCONCE** · Renaissance
9.50"W x 24.75"H x 7.50"E
Backplate: 5.25"W x 5.25"H x 1"E · Ctr/Top: 9.50"
Ctr/Btm: 15.25" · 1 – 60 Watt E12 Candelabra
Finish: RN · Damp Rated



◀ **621521RB SCONCE** · Renaissance Brown
9.50"W x 20.50"H x 4"E · Backplate:
7.5"W x 20.5"H x .75"E · Ctr/Top: 10.25"
Ctr/Btm: 10.25" · 2 – 60 Watt E12 Candelabra
Finish: RB · Damp Rated



◀ **421501RN CHANDELIER** • Renaissance
36"W x 38"H • Canopy: 5"W x 1"H • 12 - 60 Watt E12
Candelabra • Finish: RN • 10' Chain; 15' Wire

50+LBS

Additional mounting support required

▶ **121531RN-428 VANITY** • Renaissance
25"W x 9.50"H x 6.75"E • Backplate: 4.75"W x 6"H x .75"E
Ctr/Top: 3.25" • 3 - 100 Watt E26 Medium • Misty White Glass
Finish: RN • Damp Rated



▲ **121541RN-428 VANITY** • Renaissance
35"W x 9.50"H x 6.75"E • Backplate: 4.75"W x 6"H x .75"E
Ctr/Top: 3.25" • 4 - 100 Watt E26 Medium • Misty White Glass
Finish: RN • Damp Rated



◀ **421561RN CHANDELIER** · Renaissance
28"W x 28.50"H · Canopy: 5"W x 1"H · 6 – 60 Watt E12
Candelabra · Finish: RN · 10' Chain; 15' Wire



▲ **321541RN PENDANT** · Renaissance
18"W x 19.75"H · Canopy: 5"W x 1"H · 4 – 60 Watt
E12 Candelabra · Finish: RN · 10' Chain; 15' Wire



◀ **521531RN FOYER** · Renaissance
12.75"W x 29"H · Canopy: 5"W x 1"H · 3 – 60 Watt E12
Candelabra · Finish: RN · 10' Chain; 15' Wire



◀ **3606RI-125 CHANDELIER** • *Rustic Iron*
30"W x 32.50"H • Canopy: 5.25"W x 1.75"H • 6 – 100
Watt E26 Medium • Rust Scavo Glass • Finish: RI
10' Chain; 15' Wire

▶ **3601RI-125 PENDANT** • *Rustic Iron*
4.50"W x 20"H • Canopy: 5.25"W x 1.75"H • 1 – 100
Watt E26 Medium • Rust Scavo Glass • Finish: RI
10' Chain; 15' Wire



river crest *collection*

IN RUSTIC IRON



◀ **9354RI FOYER** • *Rustic Iron*
12"W x 20.50"H • Canopy: 5.25"W x 1.75"H • 4 – 60 Watt
E12 Candelabra • Finish: RI • 10' Chain; 15' Wire

▶ **2287RI CEILING** • *Rustic Iron*
24"W x 10.50"H • 3 – 60 Watt E26 Medium • Rust Scavo
Glass • Finish: RI • Damp Rated





◀ **3604RI-279 PETITE** • *Rustic Iron*
19.50"W x 21"H • Canopy: 5.25"W x 1.75"H
4 – 60 Watt E12 Candelabra • Rust Scavo Glass
Finish: RI • 5' Chain; 10' Wire



▶ **3600RI-125 CHANDELIER** • *Rustic Iron*
61"W x 70"H • Canopy: 9"W x 2.75"H • 20 – 60 Watt E26
Medium • Rust Scavo Glass • Finish: RI • 10' Chain; 15' Wire

50+LBS

Additional mounting support required

▶ **3609RI-125 CHANDELIER** · *Rustic Iron*
39"W x 44"H · Canopy: 6"W x 2"H · 9 – 60 Watt E26
Medium · Rust Scavo Glass · Finish: RI · 10' Chain;
15' Wire

50+LBS

Additional mounting support required



◀ **3602RI-125 CHANDELIER** · *Rustic Iron*
48"W x 55"H · Canopy: 6"W x 2"H · 12 – 60 Watt E26
Medium · Rust Scavo Glass · Finish: RI · 10' Chain;
15' Wire

50+LBS

Additional mounting support required



▼ **2283RI CEILING** · *Rustic Iron*
13"W x 8"H · 2 – 60 Watt E26 Medium
Rust Scavo Glass · Finish: RI · Damp Rated



▶ **1908RI-125 SCONCE** • *Rustic Iron*

9"W x 32"H x 6"E • Backplate: 5"W x 9"H x 1"E
 Ctr/Top: 9" Ctr/Btm: 23" • 1 – 100 Watt E26 Medium
 Rust Scavo Glass • Finish: RI • Damp Rated

▼ **1909RI-125 SCONCE** • *Rustic Iron*

11.50"W x 33"H x 6"E • Backplate: 5"W x 9"H x 1"E
 Ctr/Top: 12" Ctr/Btm: 21" • 2 – 100 Watt E26 Medium
 Rust Scavo Glass • Finish: RI • Damp Rated



▲ **3603RI CEILING** • *Rustic Iron*

18"W x 19"H • Canopy: 5.25"W x 1.75"H • 3 – 100 Watt
 E26 Medium Rust Scavo Glass • Finish: RI • Damp Rated



◀ **1906RI-125 SCONCE** • *Rustic Iron*

9"W x 13.50"H x 7"E • Backplate: 5"W x 9"H x 1"E
 Ctr/Top: 4.50" Ctr/Btm: 9" • 1 – 100 Watt E26 Medium
 Rust Scavo Glass • Finish: RI • Damp Rated



▲ **1903RI-125 VANITY** • *Rustic Iron*

29"W x 11.50"H x 7.50"E • Backplate: 9"W x 5"H x 1"E
 Ctr/Top: 5.75" Ctr/Btm: 6" • 3 – 100 Watt E26 Medium
 Rust Scavo Glass • Finish: RI • Damp Rated



▲ **1907RI-125 SCONCE** • *Rustic Iron*

13"W x 15"H x 7"E • Backplate: 5"W x 9"H x 1"E
 Ctr/Top: 6" Ctr/Btm: 9" • 2 – 100 Watt E26 Medium
 Rust Scavo Glass • Finish: RI • Damp Rated



riviera

collection

IN ANTIQUE SILVER



◀ **310611AS-301 PENDANT** • *Antique Silver*
12"W x 59"H • 59"H Overall Includes 6", 12" & 18"
Removable Rods • Canopy: 5"W x .75"H • 1 – 100 Watt
E26 Medium • Clear Sea Glass • Finish: AS • 1' Chain;
6' Wire

▼ **410661AS-301 CHANDELIER** • *Antique Silver*
28"W x 20.75"H • Canopy: 5"W x .75"H • 6 – 100 Watt
E26 Medium • Clear Sea Glass • Finish: AS • 10' Chain;
15' Wire



◀ **310631AS-301 PENDANT** • *Antique Silver*
24"W x 18"H • Canopy: 5"W x .75"H • 3 – 100 Watt E26
Medium • Clear Sea Glass • Finish: AS • 10' Chain;
15' Wire



rowan
collection

IN RUSTIC



◀ **511641RT FOYER** • *Rustic*
16"W x 27.75"H • Canopy: 5"W x .75"H • 4 – 60 Watt
E12 Candelabra • Finish: RT • 10' Chain; 15' Wire

▶ **411661RT-322 CHANDELIER** • *Rustic*
28"W x 30.50"H • Canopy: 5"W x .75"H • 6 – 60 Watt
E12 Candelabra • Clear Water Glass • Finish: RT
10' Chain; 15' Wire



RT-Rustic

▶ **411601RT-322 CHANDELIER** · *Rustic*
34"W x 41"H · Canopy: 5"W x .75"H · 10 – 60 Watt
E12 Candelabra · Clear Water Glass · Finish: RT
10' Chain; 15' Wire



◀ **611611RT-322 SCONCE** · *Rustic*
4.50"W x 16"H x 7.50"E · Backplate: 4.25"W x 8"H x .75"E
Ctr/Top: 12" Ctr/Btm: 4" · 1 – 60 Watt E12 Candelabra
Clear Water Glass · Finish: RT · Damp Rated



GL322 GLASS
4.5"W x 7"H

▶ **111621RT-322 VANITY** · *Rustic*

13.75"W x 10"H x 7.25"E
 Backplate: 8"W x 4.25"H x .75"E
 Ctr/Top: 7.75" Ctr/Btm: 2.25" · 2 – 60 Watt E12
 Candelabra · Clear Water Glass · Finish: RT
 Damp Rated

◀ **111631RT-322 VANITY** · *Rustic*

22"W x 10"H x 7.25"E
 Backplate: 8"W x 4.25"H x .75"E
 Ctr/Top: 7.75" Ctr/Btm: 2.25" · 3 – 60
 Watt E12 Candelabra · Clear Water Glass
 Finish: RT · Damp Rated

▲ **111641RT-322 VANITY** · *Rustic*

30.25"W x 10"H x 7.25"E · Backplate: 8"W x 4.25"H x .75"E
 Ctr/Top: 7.75" Ctr/Btm: 2.25" · 4 – 60 Watt E12 Candelabra
 Clear Water Glass · Finish: RT · Damp Rated

A living room with a chandelier, a sofa, a coffee table, and a plant. The room is bright and airy, with large windows and a patterned rug. The chandelier is a multi-tiered, gold-colored fixture with several glass shades. The sofa is a light-colored, tufted piece with patterned pillows. The coffee table is a low, gold-colored metal table with a glass top. A large green plant is on the right side of the room. The text 'seaton collection' is overlaid on the image, with 'IN SOFT GOLD' below it.

seaton

collection

IN SOFT GOLD



◀ **410861SF-302 CHANDELIER** · *Soft Gold*
29.50"W x 32"H · Canopy: 5"W x 1"H · 6 – 100 Watt E26
Medium · Clear Organic Glass · Finish: SF · Glass Column
10' Chain; 15' Wire



▶ **410801SF-302 CHANDELIER** · *Soft Gold*
36"W x 42.50"H · Canopy: 5"W x 1"H · 10 – 60 Watt E26
Medium · Clear Organic Glass · Finish: SF · Glass Column
10' Chain; 15' Wire




SF-Soft Gold


► **510842SF FOYER** · *Soft Gold*
 16"W x 26.50"H · Canopy: 5"W x 1"H · 4 – 60 Watt
 E12 Candelabra · Finish: SF · Glass Column · 10' Chain;
 15' Wire



◀ **510841SF FOYER** · *Soft Gold*
 14.75"W x 31"H · Canopy: 5"W x 1"H · 4 – 60 Watt
 E12 Candelabra · Finish: SF · Glass Column · 10' Chain;
 15' Wire

► **610811SF-660 SCONCE** · *Soft Gold*
 6.75"W x 17"H x 7.50"E
 Backplate: 4.75"W x 8"H x .75"E · Ctr/Top: 12.75"
 Ctr/Btm: 4.25" · 1 – 60 Watt E12 Candelabra · Decorative
 White Fabric Stay-Straight Shade · Finish: SF · Glass
 Column · Damp Rated





▲ **110841SF-302 VANITY** · *Soft Gold*
 34"W x 11.25"H x 5.75"E · Backplate: 6"W x 4.75"H x .75"E
 Ctr/Top: 4" Ctr/Btm: 7.25" · 4 – 100 Watt E26 Medium
 Clear Organic Glass · Finish: SF · Damp Rated



▲ **110831SF-302 VANITY** · *Soft Gold*
 26.50"W x 11.25"H x 5.75"E
 Backplate: 6"W x 4.75"H x .75"E · Ctr/Top: 7.25"
 Ctr/Btm: 4" · 3 – 100 Watt E26 Medium · Clear
 Organic Glass · Finish: SF · Damp Rated



◀ **110821SF-302 VANITY** · *Soft Gold*
 17"W x 11.25"H x 5.75"E
 Backplate: 6"W x 4.75"H x .75"E · Ctr/Top: 4"
 Ctr/Btm: 7.25" · 2 – 100 Watt E26 Medium · Clear
 Organic Glass · Finish: SF · Damp Rated



GL302 GLASS
 4.75"W x 6"H

A dining room scene featuring a wooden dining table with a dark finish, surrounded by upholstered chairs. One chair in the foreground is a light blue color with a dark blue accent and brass nailhead trim. A large, ornate chandelier hangs from the ceiling. In the background, a wooden staircase with a dark railing is visible. A large, abstract painting is on the wall. The floor is covered with a patterned rug.

sinclair
collection

IN RENAISSANCE BROWN

▶ **417461RB-372 CHANDELIER** · Renaissance Brown
32"W x 33"H · Canopy: 5"W x .75"H · 6 – 100 Watt
E26 Medium · Clear Water Glass · Finish: RB
10' Chain; 15' Wire



◀ **417401RB-372 CHANDELIER** · Renaissance Brown
39.50"W x 44.50"H · Canopy: 5"W x .75"H · 10 – 100 Watt
E26 Medium · Clear Water Glass · Finish: RB
10' Chain; 15' Wire



▶ **517441RB FOYER** • *Renaissance Brown*
18"W x 19"H • Canopy: 5"W x .75"H • 4 – 60 Watt E12
Candelabra • Finish: RB • 10' Chain; 15' Wire



◀ Shown: 517441RB with
Flush Mount Option,
18"W x 15.75"H

▶ **617411RB-372 SCONCE** • *Renaissance Brown*
5"W x 20.75"H x 7"E • Backplate: 5"W x 5"H x .75"E
Ctr/Top: 7.50" Ctr/Btm: 13.25" • 1 – 100 Watt E26
Medium • Clear Water Glass • Finish: RB • Damp Rated



Coordinates With

KINGSLEY
518741DS FOYER
 see page 195



▲ **117421RB-372 VANITY** · Renaissance Brown
 14"W x 8.50"H x 6.25"E
 Backplate: 7"W x 4.25"H x .75"E · Ctr/Top: 2"
 Ctr/Btm: 6.50" · 2 – 100 Watt E26 Medium · Clear
 Water Glass · Finish: RB · Damp Rated

▼ **117431RB-372 VANITY** · Renaissance Brown
 23.25"W x 8.50"H x 6.25"E
 Backplate: 7"W x 4.25"H x .75"E · Ctr/Top: 2"
 Ctr/Btm: 6.50" · 3 – 100 Watt E26 Medium · Clear
 Water Glass · Finish: RB · Damp Rated



▼ **117441RB-372 VANITY** · Renaissance Brown
 32.50"W x 8.50"H x 6.25"E
 Backplate: 7"W x 4.25"H x .75"E · Ctr/Top: 2"
 Ctr/Btm: 6.50" · 4 – 100 Watt E26 Medium · Clear
 Water Glass · Finish: RB · Damp Rated



stanton

collection

IN BRUSHED NICKEL,
BURNISHED BRONZE
& POLISHED NICKEL



◀ **4035BN-212 CHANDELIER** · *Brushed Nickel*
27"W x 20.50"H · Canopy: 5"W x 1"H · 5 – 100 Watt E26
Medium · Soft White Glass · Finishes: BB, BN · 5' Chain;
10' Wire



▶ **4035BB-212 CHANDELIER** · *Burnished Bronze*
27"W x 20.50"H · Canopy: 5"W x 1"H · 5 – 100 Watt E26
Medium · Soft White Glass · Finishes: BB, BN
5' Chain; 10' Wire



◀ **4035BB-207 CHANDELIER** · *Burnished Bronze*
27"W x 20.50"H · Canopy: 5"W x 1"H · 5 – 100 Watt E26
Medium · Mist Scavo Glass · Finish: BB · 5' Chain;
10' Wire





- ▲ **4034BN-212 CHANDELIER** · *Brushed Nickel*
- ▶ **4034BB-212 CHANDELIER** · *Burnished Bronze*

21"W x 18"H · Canopy: 5"W x 1"H · 3 – 100 Watt E26
Medium · Soft White Glass · Finishes: BB, BN · 5' Chain;
10' Wire

- ▶ **4034BB-207 CHANDELIER** · *Burnished Bronze*
- 21"W x 18"H · Canopy: 5"W x 1"H · 3 – 100 Watt E26
Medium · Mist Scavo Glass · Finish: BB · 5' Chain;
10' Wire



- ◀ **4031BN-212 PENDANT** · *Brushed Nickel*
- ◀ **4031BB-212 PENDANT** · *Burnished Bronze*

6.75"W x 43"H · 43" Overall Includes 6", 12" & 18"L
Removable Rods · Canopy: 5"W x 1"H · 1 – 100 Watt E26
Medium · Soft White Glass · Finishes: BB, BN
1' Chain; 6' Wire

- ◀ **4031BB-207 PENDANT** · *Burnished Bronze*
- 6.75"W x 43"H · 43" Overall Includes 6", 12" & 18"L
Removable Rods · Canopy: 5"W x 1"H · 1 – 100 Watt E26
Medium · Mist Scavo Glass · Finish: BB · 1' Chain; 6' Wire





◀ **4037BN CEILING** · *Brushed Nickel*
17"W x 10"H · Canopy: 5.50"W x 1"H · 3 – 100 Watt
E26 Medium · Soft White Glass · Finishes: BB, BN
Damp Rated



▲ **4037BB CEILING** · *Burnished Bronze*
17"W x 10"H · Canopy: 5.50"W x 1"H · 3 – 100 Watt E26
Medium · Mist Scavo Glass · Finish: BB · Damp Rated



◀ **4037BB-SW CEILING** · *Burnished Bronze*
17"W x 10"H · Canopy: 5.50"W x 1"H · 3 – 100 Watt
E26 Medium · Soft White Glass · Finishes: BB, BN
Damp Rated



▲ **4038BN PENDANT** · *Brushed Nickel*
20.50"W x 23"H · Canopy: 5"W x 1"H · 3 – 100 Watt E26
Medium · Soft White Glass · Finishes: BB, BN
5' Chain; 10' Wire



▶ **4038BB PENDANT** · *Burnished Bronze*
20.50"W x 23"H · Canopy: 5"W x 1"H · 3 – 100 Watt E26
Medium · Mist Scavo Glass · Finish: BB
5' Chain; 10' Wire

◀ **4038BB-SW PENDANT** · *Burnished Bronze*
20.50"W x 23"H · Canopy: 5"W x 1"H · 3 – 100 Watt
E26 Medium · Soft White Glass · Finishes: BB, BN
5' Chain; 10' Wire





◀ **9553BN FOYER** • *Brushed Nickel*
 22"W x 35.50"H • Canopy: 5"W x 1"H • 8 – 60
 Watt E12 Candelabra • Finishes: BB, BN, PN
 6' Chain; 10' Wire



▲ **9553PN FOYER** • *Polished Nickel*
 22"W x 35.50"H Canopy: 5"W x 1"H • 8 – 60 Watt
 E12 Candelabra • Finishes: BB, BN, PN • 6' Chain;
 10' Wire

▶ **9553BB FOYER** • *Burnished Bronze*
 22"W x 35.50"H • Canopy: 5"W x 1"H • 8 – 60
 Watt E12 Candelabra • Finishes: BB, BN, PN •
 6' Chain; 10' Wire



**4032BN-236
 FOYER**
 Includes Semi-Flush
 Mount Option
 7.25"W x 11"H



▲ **4032BN-236 FOYER** • *Brushed Nickel*
 7.25"W x 11"H • Canopy: 5.50"W x 1"H • 2 – 60 Watt
 E12 Candelabra • Clear Seeded Glass • Finishes: BB, BN
 5' Chain; 10' Wire

▶ **4032BB-236 FOYER** • *Burnished Bronze*
 7.25"W x 11"H • Canopy: 5.50"W x 1"H • 2 – 60 Watt
 E12 Candelabra • Clear Seeded Glass • Finishes: BB, BN
 5' Chain; 10' Wire



**4032BB-236
 FOYER**
 Includes Semi-Flush
 Mount Option
 7.25"W x 11"H



▼ **9552PN FOYER** · *Polished Nickel*
 16.75"W x 29"H · Canopy: 5"W x 1"H · 6 – 60 Watt E12
 Candelabra · Finishes: BB, BN, PN · 6' Chain; 10' Wire



▲ **9552BN FOYER** · *Brushed Nickel*
 16.75"W x 29"H · Canopy: 5"W x 1"H · 6 – 60 Watt E12
 Candelabra · Finishes: BB, BN, PN · 6' Chain; 10' Wire

▲ **9552BB FOYER** · *Burnished Bronze*
 16.75"W x 29"H · Canopy: 5"W x 1"H · 6 – 60 Watt E12
 Candelabra · Finishes: BB, BN, PN · 6' Chain; 10' Wire



▼ **4036BB FOYER** · *Burnished Bronze*
 10.25"W x 17"H · Canopy: 5"W x 1"H · 3 – 60 Watt E12
 Candelabra · Finishes: BB, BN, PN · 5' Chain; 10' Wire

▲ **4036PN FOYER** · *Polished Nickel*
 10.25"W x 17"H · Canopy: 5"W x 1"H · 3 – 60 Watt E12
 Candelabra · Finishes: BB, BN, PN · 5' Chain; 10' Wire

▲ **4036BN FOYER** · *Brushed Nickel*
 10.25"W x 17"H · Canopy: 5"W x 1"H · 3 – 60 Watt E12
 Candelabra · Finishes: BB, BN, PN · 5' Chain; 10' Wire



▶ **8491BB-103 SCONCE** · *Burnished Bronze*
6" W x 8" H x 7.25" E · Backplate: 5"W x 5"H x 1"E
Ctr/Top: 5.50" Ctr/Btm: 2.50" · 1 – 75 Watt E26 Medium
Soft White Glass · Finishes: BB, BN, CH · Damp Rated



steele

collection

IN BRUSHED NICKEL,
BURNISHED BRONZE
& CHROME



▲ **8491BN-103 SCONCE** · *Brushed Nickel*
6"W x 8"H x 7.25"E · Backplate: 5"W x 5"H x 1"E
Ctr/Top: 5.50" Ctr/Btm: 2.50" · 1 – 75 Watt E26 Medium
Soft White Glass · Finishes: BB, BN, CH · Damp Rated



▲ **8491CH-103 SCONCE** · *Chrome*
6"W x 8"H x 7.25"E · Backplate: 5"W x 5"H x 1"E
Ctr/Top: 5.50" Ctr/Btm: 2.50" · 1 – 75 Watt E26 Medium
Soft White Glass · Finishes: BB, BN, CH · Damp Rated

Coordinates With

HUDSON
411961PN CHANDELIER
 see page 184



CITY
319201PN CHANDELIER
 see page 131



MORGAN
4818PN CHANDELIER
 see page 243



▲ **4340BB-103 PENDANT** · *Burnished Bronze*
 6.25"W x 43.50"H · 43.50"H Overall Includes 6", 12" &
 18"L Removable Rods · Canopy: 6"W x 1"H · 1 – 75 Watt
 E26 Medium · Soft White Glass · Finishes: BB, BN
 1' Chain; 6' Wire

▲ **4340BN-103 PENDANT** · *Brushed Nickel*
 6.25"W x 43.50"H · 43.50"H Overall Includes 6", 12" &
 18"L Removable Rods · Canopy: 6"W x 1"H · 1 – 75 Watt
 E26 Medium · Soft White Glass · Finishes: BB, BN
 1' Chain; 6' Wire



◀ **8492BN-103 VANITY** · *Brushed Nickel*
 14.75"W x 8"H x 7.25"E · Backplate: 5"W x 5"H x 1"E
 Ctr/Top: 5.50" Ctr/Btm: 2.50" · 2 – 75 Watt E26 Medium
 Soft White Glass · Finishes: BB, BN, CH · Damp Rated



▲ **8492CH-103 VANITY** · *Chrome*
 14.75"W x 8"H x 7.25"E · Backplate: 5"W x 5"H x 1"E
 Ctr/Top: 5.50" Ctr/Btm: 2.50" · 2 – 75 Watt E26 Medium
 Soft White Glass · Finishes: BB, BN, CH · Damp Rated



◀ **8492BB-103 VANITY** · *Burnished Bronze*
 14.75"W x 8"H x 7.25"E · Backplate: 5"W x 5"H x 1"E
 Ctr/Top: 5.50" Ctr/Btm: 2.50" · 2 – 75 Watt E26 Medium
 Soft White Glass · Finishes: BB, BN, CH · Damp Rated



▲ **8493BN-103 VANITY** · *Brushed Nickel*
 23.25"W x 8"H x 7.25"E · Backplate: 5"W x 5"H x 1"E
 Ctr/Top: 5.50" Ctr/Btm: 2.50" · 3 – 75 Watt E26
 Medium · Soft White Glass · Finishes: BB, BN, CH
 Damp Rated



▲ **8493CH-103 VANITY** · *Chrome*
 23.25"W x 8"H x 7.25"E · Backplate: 5"W x 5"H x 1"E
 Ctr/Top: 2.50" Ctr/Btm: 5.50" · 3 – 75 Watt E26
 Medium · Soft White Glass · Finishes: BB, BN, CH
 Damp Rated



◀ **8493BB-103 VANITY** · *Burnished Bronze*
 23.25"W x 8"H x 7.25"E · Backplate: 5"W x 5"H x 1"E
 Ctr/Top: 2.50" Ctr/Btm: 5.50" · 3 – 75 Watt E26
 Medium · Soft White Glass · Finishes: BB, BN, CH
 Damp Rated



▲ **8494BN-103 VANITY** · *Brushed Nickel*
32"W x 8"H x 7.25"E · Backplate: 5"W x 5"H x 1"E
Ctr/Top: 2.50" Ctr/Btm: 5.50" · 4 – 75 Watt E26
Medium · Soft White Glass · Finishes: BB, BN, CH
Damp Rated

▼ **8494BB-103 VANITY** · *Burnished Bronze*
32"W x 8"H x 7.25"E · Backplate: 5"W x 5"H x 1"E
Ctr/Top: 5.50" Ctr/Btm: 2.50" · 4 – 75 Watt E26
Medium · Soft White Glass · Finishes: BB, BN, CH
Damp Rated



▲ **8494CH-103 VANITY** · *Chrome*
32"W x 8"H x 7.25"E · Backplate: 5"W x 5"H x 1"E
Ctr/Top: 2.50" Ctr/Btm: 5.50" · 4 – 75 Watt E26 Medium
Soft White Glass · Finishes: BB, BN, CH · Damp Rated

▶ **413561BB-326 CHANDELIER** · *Burnished Bronze*
30"W x 27.50"H · Canopy: 5"W x .75"H · 6 – 60 Watt E12
Candelabra · Clear Glass · Finishes: BB, BN
10' Chain; 15' Wire

▼ **613511BB-326 SCONCE** · *Burnished Bronze*
5.25"W x 17"H x 5"E · Backplate: 5.25"W x 10.50"H x .75"E
Ctr/Top: 6.75" Ctr/Btm: 10.25" · 1 – 60 Watt E12 Candelabra
Clear Glass · Finishes: BB, BN · Damp Rated



stella

collection

IN BRUSHED NICKEL
& BURNISHED BRONZE



▲ **613511BN-326 SCONCE** · *Brushed Nickel*
5.25"W x 17"H x 5"E · Backplate: 5.25"W x 10.50"H x .75"E
Ctr/Top: 6.75" Ctr/Btm: 10.25" · 1 – 60 Watt E12 Candelabra
Clear Glass · Finishes: BB, BN · Damp Rated

◀ **413561BN-326 CHANDELIER** · *Brushed Nickel*
30"W x 27.50"H · Canopy: 5"W x .75"H · 6 – 60 Watt E12
Candelabra · Clear Glass · Finishes: BB, BN
10' Chain; 15' Wire

▶ **413501BB-326 CHANDELIER** • *Burnished Bronze*
33"W x 34.50"H • Canopy: 5"W x .75"H • 10 – 60 Watt
E12 Candelabra • Clear Glass • Finishes: BB, BN
10' Chain; 15' Wire



◀ **413501BN-326 CHANDELIER** • *Brushed Nickel*
33"W x 34.50"H • Canopy: 5"W x .75"H • 10 – 60 Watt
E12 Candelabra • Clear Glass • Finishes: BB, BN
10' Chain; 15' Wire

DONNY OSMOND home™
BY DONNY & DEBBIE OSMOND



◀ **3874PN-496 CEILING** · *Polished Nickel*
15"W x 11"H · Canopy: 5"W x 1"H · 3 – 60 Watt E26
Medium · Decorative White Fabric Shade · Frosted Glass
Diffuser with Finial · Finish PN · Damp Rated

studio
collection
IN POLISHED NICKEL



▶ **2305PN-513 CEILING** · *Polished Nickel*
15.75"W x 7.25"H · 3 – 40 Watt E26 Medium
Decorative White Fabric Shade · Frosted Glass
Diffuser with Finial · Finish PN · Damp Rated

▶ **3875PN-495 PENDANT** • *Polished Nickel*
24"W x 57"H • 57"H Overall Includes 6", 12" & 18"L
Removable Rods • Canopy: 5"W x 1"H • 4 – 60 Watt E26
Medium • Decorative White Fabric Shade • Frosted Glass
Diffuser with Finial • Finish: PN • 1' Chain; 6' Wire



◀ **3870PN-492 PENDANT** • *Polished Nickel*
8"W x 52.50"H • 52.50"H Overall Includes 6", 12" &
18"L Removable Rods • Canopy: 5"W x 1"H • 1 – 100 Watt
E26 Medium • Decorative White Fabric Shade • Frosted
Glass Diffuser with Finial • Finish: PN • 1' Chain; 6' Wire

► **1397PN-105 VANITY** · *Polished Nickel*

13"W x 10.50"H x 6.50"E · Backplate:
5"W x 5"H x 1.25"E · Ctr/Top: 7" Ctr/Btm: 3.50"
2 – 100 Watt E26 Medium · Soft White Glass
Finish: PN · Damp Rated



▲ **1398PN-105 VANITY** · *Polished Nickel*

20.25"W x 10.50"H x 6.50"E · Backplate: 5"W x 5"H x 1.25"E
Ctr/Top: 7" Ctr/Btm: 3.50" · 3 – 100 Watt E26 Medium · Soft
White Glass · Finish: PN · Damp Rated



▲ **1399PN-105 VANITY** · *Polished Nickel*

28.25"W x 10.50"H x 6.50"E · Backplate: 5"W x 5"H x 1.25"E
Ctr/Top: 7" Ctr/Btm: 3.50" · 4 – 100 Watt E26 Medium · Soft
White Glass · Finish: PN · Damp Rated



◀ **1171PN-489 SCONCE** • *Polished Nickel*
 5"W x 13.50"H x 5.50"E • Backplate: 5"W x 5"H x 1.25"E
 Ctr/Top: 10.50" Ctr/Btm: 3" • 1 – 60 Watt E12 Candelabra
 Decorative White Fabric Shade • Finish: PN • Damp Rated

▶ **1170PN-488 SCONCE** • *Polished Nickel*
 8"W x 13.75"H x 4"E • Backplate: 6.75"W x 7.25"H x .75"E
 Ctr/Top: 5" Ctr/Btm: 8.75" • 1 – 60 Watt E26 Medium
 Decorative White Fabric Shade • Frosted Glass Diffuser
 Finish: PN • Damp Rated • **ADA**



◀ **1172PN-489 SCONCE** • *Polished Nickel*
 12.50"W x 13.50"H x 5.50"E • Backplate: 5"W x 5"H x 1.25"E
 Ctr/Top: 10.50" Ctr/Btm: 3" • 2 – 60 Watt E12 Candelabra
 Decorative White Fabric Shades • Finish: PN • Damp Rated

◀ **4597BB-622 ISLAND** • *Burnished Bronze*
37.25"W x 54.50"H x 18.25"E • 54.50"H Overall Includes 6",
12" & 18"L Removable Rods • Canopy: 8.5"L x 4.5"W x 1"H
6 – 60 Watt E12 Candelabra • Decorative Tan Fabric Shade
Finish: BB • 1' Chain; 6' Wire



taylor
collection

IN BURNISHED BRONZE
& POLISHED NICKEL

▶ **4597PN-624 ISLAND** • *Polished Nickel*
37.25"W x 54.50"H x 18.25"E • 54.50"H
Overall Includes 6", 12" & 18"L Removable
Rods • Canopy: 8.5"L x 4.5"W x 1"H • 6 – 60
Watt E12 Candelabra • Decorative White
Fabric Shade • Finish: PN • 1' Chain; 6' Wire



▼ **4594PN-592 PENDANT** • *Polished Nickel*
 24"W x 24.25"H • Canopy: 5"W x 1"H • 4 – 60 Watt E12
 Candelabra • Decorative White Fabric Shade • Finish: PN
 10' Chain; 15' Wire



**4594PN-592
 PENDANT**
 Includes Flush
 Mount Option
 24"W x 23"H



**4594BB-605
 PENDANT**
 Includes Flush
 Mount Option
 24"W x 23"H



▲ **4594BB-605 PENDANT** • *Burnished Bronze*
 24"W x 24.25"H • Canopy: 5"W x 1"H
 4 – 60 Watt E12 Candelabra • Decorative
 Tan Fabric Shade • Finish: BB • 10' Chain;
 15' Wire

▶ **4593BB-607 PENDANT** • *Burnished Bronze*
 12"W x 17.75"H • Canopy: 5"W x 1"H • 3 – 60 Watt
 E12 Candelabra • Decorative Tan Fabric Shade • Frosted
 Glass Diffuser with Finial • Finish: BB
 10' Chain; 15' Wire

◀ **4593PN-594 PENDANT** • *Polished Nickel*
 12"W x 17.75"H • Canopy: 5"W x 1"H • 3 – 60 Watt
 E12 Candelabra • Decorative White Fabric Shade • Frosted
 Glass Diffuser with Finial • Finish: PN
 10' Chain; 15' Wire



**4593PN-594
 PENDANT**
 Includes Flush
 Mount Option
 12"W x 16.25"H



**4593BB-607
 PENDANT**
 Includes Flush
 Mount Option
 12"W x 16.25"H





vineyard

collection

IN FRENCH COUNTRY



◀ **410302FC CHANDELIER** · *French Country*
 37"W x 44"H · Canopy: 5"W x 1"H · 10 – 60 Watt E12
 Candelabra · Finish: FC · Includes Decorative Fobs
 10' Chain; 15' Wire



◀ **510342FC FOYER** · *French Country*
 15"W x 28"H · Canopy: 5"W x 1"H
 4 – 60 Watt E12 Candelabra · Finish: FC
 10' Chain; 15' Wire

▲ **410362FC CHANDELIER** · *French Country*
 30"W x 35"H · Canopy: 5"W x 1"H · 6 – 60 Watt
 E12 Candelabra · Finish: FC · Includes Decorative
 Fobs · 10' Chain; 15' Wire



▼ **610321FC SCONCE** · *French Country*
 10"W x 20"H x 6.75"E · Backplate: 5"W x 5"H x .75"
 Ctr/Top: 15" Ctr/Btm: 5" · 2 – 60 Watt E12
 Candelabra · Finish: FC · Includes Decorative Fobs
 Damp Rated

▶ **510341FC FOYER** · *French Country*
 17.25"W x 29"H · Canopy: 5"W x 1"H
 4 – 60 Watt E12 Candelabra · Finish: FC
 10' Chain; 15' Wire



FC-French Country



west port
collection

IN OLD BRONZE





▲ **820181OB ISLAND** • *Old Bronze*
44"W x 71"H x 13"E • 71"H Overall Includes 6", 12" & 18"L
Removable Rods • Canopy: 22.25"L x 5"W x 1"H • 8 – 60
Watt E12 Candelabra • Finish: OB • 1' Chain; 6' Wire

Coordinates With		
<p>3711BB-135 SCONCE see page 493</p> 	<p>4548DB-577 PENDANT see page 462</p> 	<p>3533BB-134 CEILING see page 410</p> 

► **520141OB FOYER** · *Old Bronze*
12"W x 14.25"H · Canopy: 5" W x .75" H · 4 – 60 Watt
E12 Candelabra · Finish: OB · 10' Chain; 15' Wire

520141OB
SEMI-FLUSH
Includes Flush
Mount Option
12"W x 17.75"H



◀ **520142OB FOYER** · *Old Bronze*
16"W x 26.50"H · Canopy: 5" W x .75" H · 4 – 60 Watt
E12 Candelabra · Finish: OB · 10' Chain; 15' Wire



◀ **620121OB SCONCE** · *Old Bronze*

11"W x 18"H x 6.25"E · Backplate: 9"W x 18"H x .75"E
Ctr/Top: 9" Ctr/Btm: 9" · 2 – 60 Watt E12 Candelabra
Finish: OB · Damp Rated



▶ **520181OB FOYER** · *Old Bronze*

22"W x 37.75"H · Canopy: 5"W x .75"H · 8 – 60 Watt
E12 Candelabra · Finish: OB · 10' Chain; 15' Wire



OB-Old Bronze



◀ **510141BB FOYER** • *Burnished Bronze*
12"W x 14.75"H • Canopy: 5"W x .75"H • 4 – 60 Watt E12
Candelabra • Finishes: BB, WG • 10' Chain; 15' Wire

▶ **610111WG SCONCE** • *Winter Gold*
6.25"W x 18"H x 4"E • Mirror Backplate:
6.25"W x 18"H x 1"E • Ctr/Top: 9" Ctr/Btm: 9"
1 – 60 Watt E12 Candelabra • Finishes: BB, WG
Damp Rated • **ADA**



westbrook

collection

IN BURNISHED BRONZE
& WINTER GOLD



◀ **610111BB SCONCE** • *Burnished Bronze*
6.25"W x 18"H x 4"E • Mirror Backplate:
6.25"W x 18"H x 1"E • Ctr/Top: 9" Ctr/Btm: 9"
1 – 60 Watt E12 Candelabra • Finishes: BB, WG
Damp Rated • **ADA**

▶ **510141WG FOYER** • *Winter Gold*
12"W x 14.75"H • Canopy: 5"W x .75"H • 4 – 60 Watt E12
Candelabra • Finishes: BB, WG • 10' Chain; 15' Wire





◀ **510161BB FOYER** • *Burnished Bronze*
16"W x 26.75"H • Canopy: 5"W x .75"H
6 – 60 Watt E12 Candelabra • Finishes:
BB, WG • 10' Chain; 15' Wire

Coordinates With

ALEXANDER
4746BB-000 CHANDELIER
see page 19



ALEXANDER
8073WG CEILING
see page 25



▶ **510161WG FOYER** • *Winter Gold* • 16"W x 26.75"H
Canopy: 5"W x .75"H • 6 – 60 Watt E12 Candelabra
Finishes: BB, WG • 10' Chain; 15' Wire



▶ **410182BB-657 CHANDELIER** · *Burnished Bronze*
42.50"W x 26.50"H x 25"E · Canopy: 5"W x .75"H
8 – 60 Watt E12 Candelabra · Decorative White Fabric
Stay-Straight Shades · Finishes: BB, WG · K9 Crystal
10' Chain; 15' Wire

SH657 SHADE
11.5"W x 5.5"H
Stay-Straight
Shade



◀ **410182WG-657 CHANDELIER** · *Winter Gold*
42.50"W x 26.50"H x 25"E · Canopy: 5"W x .75"H
8 – 60 Watt E12 Candelabra · Decorative White Fabric
Stay-Straight Shades · Finishes: BB, WG · K9 Crystal
10' Chain; 15' Wire



► **410181BB-657 CHANDELIER** • *Burnished Bronze*
28"W x 23.50"H • Canopy: 5"W x 1"H • 8 – 60 Watt
E12 Candelabra • Decorative White Fabric Stay-Straight
Shades • Finishes: BB, WG • K9 Crystal • 10' Chain;
15' Wire



◄ **410181WG-657 CHANDELIER** • *Winter Gold*
28"W x 23.50"H • Canopy: 5"W x 1"H • 8 – 60 Watt
E12 Candelabra • Decorative White Fabric Stay-Straight
Shades • Finishes: BB, WG • K9 Crystal • 10' Chain;
15' Wire





windsor
collection

IN SOFT GOLD

▼ **413861SF CHANDELIER** · *Soft Gold*

28.50"W x 29"H · Canopy: 5"W x 1"H · 6 – 60 Watt
E12 Candelabra · Finish: SF · Clear Glass Adornments
10' Chain; 15' Wire



▲ **413801SF CHANDELIER** · *Soft Gold*

36"W x 39"H · Canopy: 5"W x 1"H · 10 – 60 Watt
E12 Candelabra · Finish: SF · Clear Glass Adornments
10' Chain; 15' Wire

◀ **513842SF FOYER** · *Soft Gold*

16"W x 25.50"H · Canopy: 5"W x 1"H
4 – 60 Watt E12 Candelabra · Finish: SF
Clear Glass Adornments · 10' Chain;
15' Wire



▶ **513841SF FOYER** · *Soft Gold*

15.75"W x 29.50"H · Canopy: 5"W x 1"H
4 – 60 Watt E12 Candelabra · Finish: SF
Clear Glass Adornments · 10' Chain;
15' Wire

◀ **613811SF-654 SCONCE** · *Soft Gold*

6"W x 24"H x 7.50"E · Backplate:
5"W x 10"H x .50"E · Ctr/Top: 11.50"
Ctr/Btm: 12.50" · 1 – 60 Watt E12
Candelabra · Decorative White Fabric Shade
Finish: SF · Clear Glass Adornment
Damp Rated



SH654 SHADE
6"W x 4.75"H
Stay-Straight
Shade





wright
collection

IN POLISHED NICKEL

▶ **420461PN CHANDELIER** · *Polished Nickel*
 28.75"W x 29.50"H · Canopy: 5"W x .75"H · 6 – 60 Watt
 E12 Candelabra · Finish: PN · 10' Chain; 15' Wire



◀ **420401PN CHANDELIER** · *Polished Nickel*
 35"W x 43.50"H · Canopy: 5"W x .75"H · 10 – 60 Watt
 E12 Candelabra · Finish: PN · 10' Chain; 15' Wire

▼ **520443PN FOYER** · *Polished Nickel*
 15"W x 27"H · Canopy: 5"W x .75"H · 4 – 60 Watt E12
 Candelabra · Finish: PN · 10' Chain; 15' Wire

▼ **520441PN FOYER** · *Polished Nickel*
 12"W x 18"H · Canopy: 5"W x .75"H · 4 – 60 Watt E12
 Candelabra · Finish: PN · 10' Chain; 15' Wire

◀ **520442PN FOYER**
Polished Nickel
 15"W x 28.50"H · Canopy:
 5"W x .75"H · 4 – 60 Watt E12
 Candelabra · Finish: PN
 10' Chain; 15' Wire



A rustic interior space featuring a stone wall, a thatched roof, a chandelier, and a large window. The room is filled with natural light, and the overall aesthetic is warm and traditional. The chandelier is a multi-tiered, wrought-iron fixture with several candle-style lights. The window is a large, multi-paned unit with a dark wood frame, offering a view of a lush green landscape. A small table with a decorative iron base and a white cushioned stool are also visible in the room.

wyatt
collection

IN SURREY



◀ **4254SY-000 PETITE** · *Surrey*

20"W x 22.50"H · Canopy: 5.50"W x 2.25"H · 4 – 60 Watt
E12 Candelabra · Finish: SY · 10' Chain; 15' Wire

▼ **4256SY-000 CHANDELIER** · *Surrey*

49.50"W x 55"H · Canopy: 6.25"W x 2.25"H · 16 – 60
Watt E12 Candelabra · Finish: SY · 10' Chain; 15' Wire

50+LBS

Additional mounting support required



SY-Surrey



▶ **4252SY-000 SCONCE** · *Surrey*
8"W x 14.50"H x 5"E · Backplate: 6"W x 6"H x 1.25"E
Ctr/Top: 5.25" Ctr/Btm: 9.25" · 2 – 60 Watt E12
Candelabra · Finish: SY · Damp Rated

◀ **4251SY-000 SCONCE** · *Surrey*
6"W x 15"H x 5.5"E · Backplate: 6"W x 6"H x 1.25"E
Ctr/Top: 8.25" Ctr/Btm: 6.75" · 1 – 60 Watt E12
Candelabra · Finish: SY · Damp Rated



▶ **2067SY CEILING** · *Surrey*
16.50"W x 6.50"H · 3 – 60 Watt E26 Medium
Misty White Glass · Finish: SY · Damp Rated

◀ **4253SY CEILING** · *Surrey*
16.50"W x 13.50"H · Canopy: 4.25"W x 1"H
3 – 60 Watt E26 Medium · Misty White Glass
Finish: SY · Damp Rated



► **4255SY-000 CHANDELIER** · *Surrey*
27.75"W x 27.75"H · Canopy: 5.50"W x 2.25"H · 6 – 60
Watt E12 Candelabra · Finish: SY · 10' Chain; 15' Wire



◄ **4250SY-000 CHANDELIER** · *Surrey*
36"W x 36.50"H · Canopy: 5.50"W x 2.25"H · 10 – 60
Watt E12 Candelabra · Finish: SY · 10' Chain; 15' Wire



▶ **9001SY FOYER** · *Surrey*
13.50"W x 18"H · Canopy: 5.25"W x 2.25"H · 3 – 60 Watt
E12 Candelabra · Finish: SY · 10' Chain; 15' Wire

9001SY FOYER
Includes Flush
Mount Option
13.50"W x 17.50"H



▼ **9002SY FOYER** · *Surrey*
24"W x 38.50"H · Canopy: 5.25"W x 2.25"H · 6 – 60 Watt
E12 Candelabra · Finish: SY · 10' Chain; 15' Wire



▲ **9003SY FOYER** · *Surrey*
30"W x 45.50"H · Canopy: 5.25"W x 2.25"H · 8 – 60 Watt
E12 Candelabra · Finish: SY · 10' Chain; 15' Wire

► **8012SY-123 VANITY** · *Surrey*

17"W x 8.50"H x 8"E · Backplate: 10.75"W x 5.50"H x 1"E
 Ctr/Top: 2.50" Ctr/Btm: 6" · 2 – 100 Watt E26 Medium
 Misty White Glass Finish: SY · Damp Rated



▼ **8013SY-123 VANITY** · *Surrey*

25.50"W x 8.50"H x 9.50"E · Backplate: 10.75"W x 5.50"H x 1"E
 Ctr/Top: 6" Ctr/Btm: 2.50" · 3 – 100 Watt E26 Medium · Misty
 White Glass · Finish: SY · Damp Rated



▲ **8014SY-123 VANITY** · *Surrey*

32.25"W x 8.50"H x 9.50"E · Backplate: 10.75"W x 5.50"H x 1"E
 Ctr/Top: 2.50" Ctr/Btm: 6" · 4 – 100 Watt E26 Medium · Misty
 White Glass · Finish: SY · Damp Rated



zander

collection

IN AGED BRASS
& POLISHED NICKEL



◀ **421902AD CHANDELIER** · *Aged Brass*
36"W x 35.75"H · Canopy: 5"W x .75"H · 16 – 60 Watt
E12 Candelabra · Finish: AD · 10' Chain; 15' Wire



▶ **521981AD FOYER** · *Aged Brass*
16"W x 26"H · Canopy: 5"W x .75"H · 8 – 60 Watt
E12 Candelabra · Finish: AD · 10' Chain; 15' Wire



AD-Aged Brass



◀ **621931AD SCONCE** · *Aged Brass*

9"W x 20"H x 3.50"E · Backplate: 5"W x 8.25"H x .75"E
Ctr/Top: 15.50" Ctr/Btm: 4.50" · 3 – 60 Watt E12 Candelabra
Finishes: AD, PN · Damp Rated · **ADA**

◀ **621931PN SCONCE** · *Polished Nickel*

9"W x 20"H x 3.50"E · Backplate: 5"W x 8.25"H x .75"E
Ctr/Top: 15.50" Ctr/Btm: 4.50" · 3 – 60 Watt E12 Candelabra
Finishes: AD, PN · Damp Rated · **ADA**

▶ **421903AD CHANDELIER** · *Aged Brass*

42.50"W x 94"H · 94"H Overall Includes 6", 12" & 18"L
Removable Rods · Canopy: 5"W x .75"H · 20 – 60 Watt
E12 Candelabra · Finish: AD · 1' Chain; 6' Wire



► **421901AD CHANDELIER** · *Aged Brass*
26.75"W x 83"H · 83"H Overall
Includes 6", 12" & 18"L Removable Rods
Canopy: 5"W x .75"H · 12 – 60 Watt E12
Candelabra · Finish: AD · 1' Chain; 6' Wire



Coordinates With

DAWSON
519342AD FOYER
see page 148



MID-CENTURY
121131AD-426 VANITY
see page 225



3533AD-134
CEILING
see page 00



◄ **821901AD ISLAND** · *Aged Brass*
46"W x 57.50"H x 11.50"E · 57.50"H Overall
Includes 6", 12" & 18"L Removable Rods
Canopy: 22.5"L x 5"W x 1"H · 18 – 60 Watt
E12 Candelabra · Finish: AD · 1' Chain; 6' Wire



► Center View





outdoor
collection



OUTDOOR

Ashford	348-349
Bolton	350-351
Brookwood	352-353
Carriage House	354-356
Collins Hill	357
Creekside	358-361
Dylan	362-365
French Country	366-367
Gentry	368-369
Grant Park LED	370-371
Harbour	372-373
Inman Park	374-376
Lakeshore	377
Lanier LED	378-379
Main Street	380-383
Mission Hills	384-385
Preston	386-387
Spencer	388-389
Sutter Creek	390-391
Townsende	392-393
Westridge	394-395
Assorted LED	396-397
Assorted Styles & Finishes	398-399



▲ **9782OB WALL LANTERN** · *Old Bronze*
 7.75"W x 20.25"H x 11.25"E · Backplate:
 5"W x 8.75"H x 1"E · Ctr/Top: 8"
 Ctr/Btm: 12.25" · 2 – 60 Watt E12 Candelabra
 Water Glass · Finishes: BK, OB · Wet Rated

▼ **9783OB WALL LANTERN** · *Old Bronze*
 10"W x 24.25"H x 14"E · Backplate:
 6"W x 11.25"H x 1"E · Ctr/Top: 10.5"
 Ctr/Btm: 13.75" · 3 – 60 Watt E12 Candelabra
 Water Glass · Finishes: BK, OB · Wet Rated



▲ **9784OB WALL LANTERN** · *Old Bronze*
 12.25"W x 29"H x 17"E · Backplate:
 7"W x 12.75"H x 1.25"E · Ctr/Top: 13"
 Ctr/Btm: 16" · 4 – 60 Watt E12
 Candelabra · Water Glass · Finishes:
 BK, OB · Wet Rated



◀ **9785OB POST
 LANTERN** · *Old Bronze*
 10.25"W x 22.50"H
 3 – 60 Watt E12
 Candelabra
 Water Glass
 Finishes: BK, OB
 Wet Rated
 Fits 3" Post (sold
 separately)



▲ **9786OB HANGING LANTERN**
Old Bronze · 10.25"W x 21.75"H · Canopy:
 5"W x 1"H · 3 – 40 Watt E12 Candelabra
 Water Glass · Finishes: BK, OB
 3' Chain; 10' Wire · Damp Rated



◀ **9805OB POST
 LANTERN** · *Old Bronze*
 3"W x 83"H
 Finish: OB



▲ **9781OB WALL LANTERN** · *Old Bronze*
 7"W x 15.25"H x 8.50"E · Backplate:
 4.75"W x 6"H x 1"E · Ctr/Top: 5.5"
 Ctr/Btm: 9.75" · 2 – 60 Watt E12
 Candelabra · Water Glass · Finishes:
 BK, OB · Wet Rated



▼ **9783BK WALL LANTERN** · Black
 10"W x 24.25"H x 14"E · Backplate:
 6"W x 11.25"H x 1"E · Ctr/Top: 10.5"
 Ctr/Btm: 13.75" · 3 – 60 Watt E12 Candelabra
 Water Glass · Finishes: BK, OB · Wet Rated



▲ **9782BK WALL LANTERN** · Black
 7.75"W x 20.25"H x 11.25"E · Backplate:
 5"W x 8.75"H x 1"E · Ctr/Top: 8"
 Ctr/Btm: 12.25" · 2 – 60 Watt E12 Candelabra
 Water Glass · Finishes: BK, OB · Wet Rated

▲ **9784BK WALL LANTERN** · Black
 12.25"W x 29"H x 17"E · Backplate:
 7"W x 12.75"H x 1.25"E · Ctr/Top: 13"
 Ctr/Btm: 16" · 4 – 60 Watt E12 Candelabra
 Water Glass · Finishes: BK, OB · Wet Rated



◀ **9785BK POST LANTERN** · Black
 10.25"W x 22.50"H
 3 – 60 Watt E12
 Candelabra
 Water Glass
 Finishes: BK, OB
 Wet Rated
 Fits 3" Post (sold separately)



▲ **9781BK WALL LANTERN**
 Black · 7"W x 15.25"H x 8.50"E
 Backplate: 4.75"W x 6"H x 1"E
 Ctr/Top: 5.5" Ctr/Btm: 9.75"
 2 – 60 Watt E12 Candelabra
 Water Glass · Finishes: BK, OB
 Wet Rated



▲ **9786BK HANGING LANTERN**
 Black · 10.25"W x 21.75"H
 Canopy: 5"W x 1"H · 3 – 40 Watt E12
 Candelabra · Water Glass · Finishes:
 BK, OB · 3' Chain; 10' Wire · Damp Rated



◀ **9805BK POST LANTERN**
 Black
 3"W x 83"H
 Finish: BK



▲ **9666OB HANGING LANTERN** · *Old Bronze*
11.75"W x 18.75"H x 6.75"E · Canopy: 5"W x 1"H
2 – 60 Watt E12 Candelabra · Antique Glass
Finish: OB · 10' Chain; 15' Wire
Damp Rated

◀ **9665OB POST LANTERN** · *Old Bronze*
11.75"W x 19.25"H x 6.75"E · 3 – 60 Watt E12
Candelabra · Antique Glass · Finish: OB
Wet Rated · Fits 3" Post (sold separately)

◀ **9805OB POST** · *Old Bronze*
3"W x 83"H · Finish: OB



◀ **9661OB WALL LANTERN** · *Old Bronze*
7.50"W x 11"H x 4.50"E · Backplate:
6.50"W x 8.75"H x .25"E · Ctr/Top: 5.50"
2 – 60 Watt E12 Candelabra · Antique Glass
Finish: OB · Wet Rated



▲ **9662OB WALL LANTERN** · *Old Bronze*
9.25"W x 13.75"H x 5.50"E · Backplate:
8.25"W x 11"H x .50"E · Ctr/Top: 7"
Ctr/Btm: 6.75" · 2 – 60 Watt E12 Candelabra
Antique Glass · Finish: OB · Wet Rated



▶ **9663OB WALL LANTERN** · *Old Bronze*
11.5"W x 17.25"H x 6.75"E · Backplate:
10.25"W x 13.5"H x .50"E · Ctr/Top: 8.75"
3 – 60 Watt E12 Candelabra · Antique Glass
Finish: OB · Wet Rated



▲ **9968BB CEILING**
Burnished Bronze · 11.50"W x 12.25"H
 3 – 60 Watt E12 Candelabra · Antique
 Glass · Finishes: BB, BK · Damp Rated



▲ **9962BB WALL LANTERN**
Burnished Bronze
 9"W x 18.75"H x 10.25"E · Backplate:
 4.75"W x 12.75"H x 1.25"E · Ctr/Top:
 12.50" Ctr/Btm: 6" · 2 – 60 Watt
 E12 Candelabra · Antique Glass
 Finishes: BB, BK · Wet Rated



▲ **9961BB WALL LANTERN**
Burnished Bronze
 7"W x 13.75"H x 8.25"E · Backplate:
 4.75"W x 8"H x 1.25"E · Ctr/Top: 4"
 Ctr/Btm: 9.75" · 1 – 100 Watt E26
 Medium · Antique Glass · Finishes:
 BB, BK · Wet Rated



◀ **9967BB POST LANTERN**
Burnished Bronze
 11.50"W x 24"H · 3 – 60 Watt E12
 Candelabra · Antique Glass
 Finishes: BB, BK · Wet Rated
 Fits 3" Post (sold separately)

◀ **9805BB POST** · *Burnished Bronze*
 3"W x 83"H · Finish: BB



▲ **9963BB WALL LANTERN**
Burnished Bronze
 11.50"W x 25"H x 12.50"E
 Backplate: 4.75"W x 15"H x 1.25"E
 Ctr/Top: 17" Ctr/Btm: 8" · 3 – 60
 Watt E12 Candelabra · Antique Glass
 Finishes: BB, BK · Wet Rated



▲ **9968BK CEILING** · Black
11.50"W x 12.25"H · 3 – 60 Watt E12
Candelabra · Antique Glass · Finishes:
BB, BK · Damp Rated



▲ **9962BK WALL LANTERN** · Black
9"W x 18.75"H x 10.25"E · Backplate:
4.75"W x 12.75"H x 1.25"E · Ctr/Top:
12.50" Ctr/Btm: 6.50" · 2 – 60 Watt
E12 Candelabra · Antique Glass
Finishes: BB, BK · Wet Rated



▲ **9961BK WALL LANTERN** · Black
7"W x 13.75"H x 8.25"E · Backplate:
4.75"W x 8"H x 1.25"E · Ctr/Top: 4"
Ctr/Btm: 9.75" · 1 – 100 Watt E26
Medium · Antique Glass · Finishes:
BB, BK · Wet Rated



◀ **9967BK POST LANTERN** · Black
11.50"W x 24"H · 3 – 60 Watt E12
Candelabra · Antique Glass
Finishes: BB, BK · Wet Rated
Fits 3" Post (sold separately)

◀ **9805BK POST** · Black
3"W x 83"H · Finish: BK



▲ **9963BK WALL LANTERN** · Black
11.50"W x 25"H x 12.50"E · Backplate:
4.75"W x 15"H x 1.25"E · Ctr/Top: 17"
Ctr/Btm: 8" · 3 – 60 Watt E12 Candelabra
Antique Glass · Finishes: BB, BK
Wet Rated

carriage house | IN BLACK & OLD BRONZE

▼ **9723OB WALL LANTERN** · *Old Bronze*

11"W x 36"H x 13.50"E · Backplate:
5"W x 19.75"H x 1"E · Ctr/Top: 20"
Ctr/Btm: 16" · 3 – 60 Watt E12 Candelabra
Clear Glass · Finishes: BK, OB · Wet Rated



◀ **9723BK WALL LANTERN** · *Black*

11"W x 36"H x 13.50"E · Backplate:
5"W x 19.75"H x 1"E · Ctr/Top: 20"
Ctr/Btm: 16" · 3 – 60 Watt E12
Candelabra · Clear Glass · Finishes:
BK, OB · Wet Rated



**9723OB & 9723BK
WALL LANTERN**
Shown Without
Included Top Scroll

▶ **9726OB WALL LANTERN** · *Old Bronze*

8"W x 15"H x 9.50"E · Backplate:
5"W x 9"H x 1"E · Ctr/Top: 6" Ctr/Btm: 9"
1 – 100 Watt E26 Medium · Clear Glass
Finishes: BK, OB · Wet Rated



▲ **9726BK WALL LANTERN** · *Black*

8"W x 15"H x 9.50"E · Backplate:
5"W x 9"H x 1"E · Ctr/Top: 6" Ctr/Btm: 9"
1 – 100 Watt E26 Medium · Clear Glass
Finishes: BK, OB · Wet Rated



◀ **9721OB WALL LANTERN** · *Old Bronze*
8"W x 23"H x 10"E · Backplate:
5"W x 13.75"H x 1"E · Ctr/Top: 14.75"
Ctr/Btm: 8.25" · 1 – 100 Watt E26 Medium
Clear Glass · Finishes: BK, OB · Wet Rated



▶ **9721BK WALL LANTERN** · *Black*
8"W x 23"H x 10"E · Backplate:
5"W x 13.75"H x 1"E · Ctr/Top: 14.75"
Ctr/Btm: 8.25" · 1 – 100 Watt E26 Medium
Clear Glass · Finishes: BK, OB · Wet Rated



**9721OB & 9721BK
WALL LANTERN**
Shown Without
Included Top Scroll



◀ **9722OB WALL LANTERN** · *Old Bronze*
9.50"W x 27"H x 11.50"E · Backplate:
5"W x 15"H x 1"E · Ctr/Top: 15.75"
Ctr/Btm: 11.25" · 2 – 60 Watt E12
Candelabra · Clear Glass · Finishes:
BK, OB · Wet Rated



▶ **9722BK WALL LANTERN** · *Black*
9.50"W x 27"H x 11.50"E · Backplate:
5"W x 15"H x 1"E · Ctr/Top: 15.75"
Ctr/Btm: 11.25" · 2 – 60 Watt E12
Candelabra · Clear Glass · Finishes:
BK, OB · Wet Rated



**9722OB & 9722BK
WALL LANTERN**
Shown Without
Included Top Scroll



◀ **9724OB HANGING LANTERN**
Old Bronze · 9.50"W x 23"H · Canopy:
5"W x 1"H · 3 – 40 Watt E12 Candelabra
Clear Glass · Finishes: BK, OB · 6' Chain;
10' Wire · Damp Rated



◀ **9724BK HANGING LANTERN** · *Black*
9.50"W x 23"H · Canopy: 5"W x 1"H
3 – 40 Watt E12 Candelabra · Clear Glass
Finishes: BK, OB · 6' Chain; 10' Wire
Damp Rated



▶ **9725BK POST LANTERN** · *Black*
9.50"W x 24"H · 3 – 60 Watt E12
Candelabra · Clear Glass · Finishes:
BK, OB · Wet Rated
Fits 3" Post (sold separately)

▶ **9805BK POST** · *Black*
3"W x 83"H · Finish: BK

◀ **9725OB POST LANTERN**
Old Bronze · 9.50"W x 24"H
3 – 60 Watt E12 Candelabra
Clear Glass · Finishes: BK, OB
Wet Rated · Fits 3"
Post (sold separately)

◀ **9805OB POST** · *Old Bronze*
3"W x 83"H · Finish: OB



▶ **9062NB WALL LANTERN**

New Bronze • 10"W x 20"H x 6"E
 Backplate: 8.5"W x 8.75"H x .50"E
 Ctr/Top: 16.25" Ctr/Btm: 4" • 2 – 60
 Watt E12 Candelabra • Antique Glass
 Finish: NB • Wet Rated



▶ **9061NB WALL LANTERN**

New Bronze • 8"W x 16.25"H x 5"E
 Backplate: 7"W x 7"H x .50"E
 Ctr/Top: 12.5" Ctr/Btm: 1.75"
 1 – 100 Watt E26 Medium
 Antique Glass • Finish: NB
 Wet Rated



▼ **9063NB WALL LANTERN** • *New Bronze*

12"W x 25"H x 6.75"E • Backplate:
 10.50"W x 10.50"H x .50"E • Ctr/Top: 19"
 Ctr/Btm: 6" • 3 – 60 Watt E12 Candelabra
 Antique Glass • Finish: NB • Wet Rated



▲ **9066NB POST LANTERN**

New Bronze • 12"W x 24.5"H
 3 – 60 Watt E12 Candelabra
 Antique Glass • Finish: NB
 Wet Rated • Fits 3" Post
 (sold separately)

◀ **9805OB POST** • *Old Bronze*

3"W x 83"H • Finish: OB

creekside
collection

IN BLACK & OLD BRONZE



◀ **9604OB**
HANGING LANTERN
Old Bronze
▶ **9604BK**
HANGING LANTERN
Black

13"W x 17.50"H • Canopy: 5"W x 1"H
 1 – 100 Watt E26 Medium • Clear Seeded
 Glass • Finishes: BK, OB • 3' Chain; 5' Wire
 Damp Rated



▲ **9603OB WALL LANTERN**
Old Bronze • 13"W x 18.50"H x 15"E
 Backplate: 7.75"W x 7.75"H x 1.50"E
 Ctr/Top: 5.25" Ctr/Btm: 13.25"
 1 – 100 Watt E26 Medium
 Clear Seeded Glass • Finishes:
 BK, OB • Wet Rated



▶ **9603BK WALL LANTERN** • *Black*
 13"W x 18.50"H x 15"E • Backplate:
 7.75"W x 7.75"H x 1.50"E
 Ctr/Top: 5.25" Ctr/Btm: 13.25"
 1 – 100 Watt E26 Medium
 Clear Seeded Glass • Finishes:
 BK, OB • Wet Rated



▶ **9602BK WALL LANTERN** · *Black*
11"W x 16.25"H x 12"E · Backplate:
6"W x 6"H x 1"E · Ctr/Top: 4.75" Ctr/Btm:
11.50" · 1 – 100 Watt E26 Medium · Clear
Seeded Glass · Finishes: BK, OB · Wet Rated



◀ **9602OB WALL LANTERN** · *Old Bronze*
11"W x 16.25"H x 12"E · Backplate:
6"W x 6"H x 1"E · Ctr/Top: 4.75" Ctr/Btm:
11.50" · 1 – 100 Watt E26 Medium · Clear
Seeded Glass · Finishes: BK, OB · Wet Rated



▲ **9601OB WALL LANTERN** · *Old Bronze*
8.25"W x 13.25"H x 9"E · Backplate:
5"W x 5"H x 1"E · Ctr/Top: 4" Ctr/Btm: 9.25"
1 – 100 Watt E26 Medium · Clear Seeded Glass
Finishes: BK, OB · Wet Rated



▲ **9601BK WALL LANTERN** · *Black*
8.25"W x 13.25"H x 9"E · Backplate:
5"W x 5"H x 1"E · Ctr/Top: 4" Ctr/Btm: 9.25"
1 – 100 Watt E26 Medium · Clear Seeded Glass
Finishes: BK, OB · Wet Rated



◀ **9607OB CEILING** • *Old Bronze*
8.25"W x 12"H • Canopy: 5"W x 1.25"H
1 – 100 Watt E26 Medium • Clear Seeded
Glass • Finishes: BK, OB • Damp Rated



◀ **9607BK CEILING** • *Black*
8.25"W x 12"H • Canopy: 5"W x 1.25"H
1 – 100 Watt E26 Medium • Clear Seeded
Glass • Finishes: BK, OB • Damp Rated



◀ **9671OB WALL LANTERN** • *Old Bronze*
8.25"W x 11.25"H x 9.50"E • Backplate:
5"W x 5"H x 1"E • Ctr/Top: 4" Ctr/Btm: 7.25"
1 – 75 Watt E26 Medium • Clear Glass
Finishes: BK, OB • Wet Rated



▶ **9671BK WALL LANTERN** • *Black*
8.25"W x 11.25"H x 9"E • Backplate:
5"W x 5"H x 1"E • Ctr/Top: 4"
Ctr/Btm: 7.25" • 1 – 75 Watt E26 Medium
Clear Glass • Finishes: BK, OB • Wet Rated



◀ **9677OB CEILING** • *Old Bronze*
◀ **9677BK CEILING** • *Black*
8.25"W x 10"H • Canopy: 5"W x 1.25"H
1 – 75 Watt E26 Medium • Clear Glass
Finishes: BK, OB • Damp Rated





The image shows an outdoor patio area with a rustic stone wall and a wooden ceiling. Two black metal hanging lanterns are suspended from the ceiling. In the foreground, there is a dark wicker sofa with white cushions and a wooden coffee table. A large potted plant is visible in the background. The text 'dylan collection' is centered in the image, with 'dylan' in a large serif font and 'collection' in a smaller italicized serif font.

dylan

collection

IN OLD BRONZE



◀ **9567OB CEILING** · *Old Bronze*
 16"W x 10"H · Canopy: 5"W x 1"H
 3 – 100 Watt E26 Medium · Antique
 Glass · Frosted Glass Diffuser
 Finish: OB · Damp Rated



▶ **9568OB PENDANT** · *Old Bronze*
 22"W x 13"H · Canopy: 5"W x 1"H
 4 – 100 Watt E26 Medium
 Antique Glass · Finish: OB
 3' Chain; 5' Wire · Damp Rated



◀ **9562OB WALL LANTERN** · *Old Bronze*
 9.50"W x 15.25"H x 10.75"E · Backplate:
 5"W x 5"H x 1"E · Ctr/Top: 7.5"
 Ctr/Btm: 7.75" · 1 – 100 Watt E26
 Medium · Antique Glass
 Finish: OB · Wet Rated

▼ **9561OB WALL LANTERN** · *Old Bronze*
 7.50"W x 12.50"H x 8.75"E · Backplate:
 5"W x 5"H x 1"E · Ctr/Top: 6.5"
 Ctr/Btm: 6" · 1 – 100 Watt E26
 Medium · Antique Glass
 Finish: OB · Wet Rated



▶ **9563OB WALL LANTERN**
Old Bronze
 11.50"W x 18.50"H x 13.25"E
 Backplate: 6"W x 6"H x 1"E
 Ctr/Top: 9.5" Ctr/Btm: 9"
 1 – 100 Watt E26 Medium · Antique
 Glass · Finish: OB · Wet Rated



◀ **9565OB POST LANTERN** · *Old Bronze*
 11.50"W x 18"H · 1 – 100 Watt E26 Medium
 Antique Glass · Finish: OB · Wet Rated
 Fits 3" Post (sold separately)

◀ **9805OB POST** · *Old Bronze*
 3"W x 83"H · Finish: OB

▶ **9564OB HANGING LANTERN**
Old Bronze · 11.50"W x 17"H
 Canopy: 5"W x 1"H · 1 – 100 Watt
 E26 Medium · Antique Glass
 Finish: OB · 3' Chain; 5' Wire
 Damp Rated



▶ **9611OB WALL LANTERN** · *Old Bronze*

7.50"W x 12.50"H x 8.75"E · Backplate:

5"W x 5"H x 1"E · Ctr/Top: 6.5"

Ctr/Btm: 6" · 1 – 100 Watt E26

Medium · Bronze Brass Screen · Finish: OB

Wet Rated



▼ **9613OB WALL LANTERN** · *Old Bronze*

11.50"W x 18.50"H x 13.25"E · Backplate:

6"W x 6"H x 1"E · Ctr/Top: 9.5"

Ctr/Btm: 9" · 1 – 100 Watt E26 Medium Bronze

Brass Screen · Finish: OB · Wet Rated

▲ **9612OB WALL LANTERN**

Old Bronze · 9.50"W x 15.25"H x 10.75"E

Backplate: 5"W x 5"H x 1"E · Ctr/Top: 7.5"

Ctr/Btm: 7.75" · 1 – 100 Watt E26

Medium · Bronze Brass Screen · Finish: OB · Wet Rated



▶ **9615OB POST LANTERN**

Old Bronze · 11.50"W x 18"H

1 - 100 Watt E26 Medium · Bronze Brass

Screen · Finish: OB · Wet Rated

Fits 3" Post (sold separately)

▶ **9805OB POST** · *Old Bronze*


3"W x 83"H · Finish: OB



► **9618OB PENDANT** • *Old Bronze*
 22"W x 13"H • Canopy: 5"W x 1"H • 4 – 100
 Watt E26 Medium • Bronze Brass Screen
 Finish: OB • 3' Chain; 5' Wire • Damp Rated



Close-up View
 of Bronze
 Brass Screen



▲ **9617OB CEILING** • *Old Bronze*
 16"W x 9.50"H Canopy: 5"W x 1"H • 3 – 100 Watt E26
 Medium • Bronze Brass Screen • Screen Diffuser
 Finish: OB • Damp Rated

► **9614OB HANGING LANTERN** • *Old Bronze*
 11.50"W x 17"H • Canopy: 5"W x 1"H
 1 - 100 Watt E26 Medium • Bronze Brass Screen
 Finish: OB • 3' Chain; 5' Wire • Wet Rated



▼ **9863BK WALL LANTERN** · Black

7.50"W x 22.50"H x 11"E

Backplate: 4.50"W x 13.50"H x 1"E

Ctr/Top: 14.25" Ctr/Btm: 8.25" · 3 – 60

Watt E12 Candelabra · Clear Glass

Finish: BK · Wet Rated



▶ **9867BK WALL LANTERN** · Black

6.50"W x 19"H x 9.50"E

Backplate: 4.50"W x 11.75"H x 1"E

Ctr/Top: 11" Ctr/Btm: 8" · 1 – 100

Watt E26 Medium · Clear Glass

Finish: BK · Wet Rated



▶ **9866BK WALL LANTERN** · Black

6.50"W x 16"H x 8.50"E

Backplate: 4.50"W x 7"H x 1"E

Ctr/Top: 5.25" Ctr/Btm: 10.75"

1 – 100 Watt E26 Medium · Clear Glass

Finish: BK · Wet Rated





◀ **9865BK POST LANTERN** · Black
8"W x 21"H · 3 – 60 Watt E12 Candelabra
Clear Glass · Finish: BK · Wet Rated
Fits 3" Post (sold separately)

◀ **9805BK POST** · Black
3"W x 83"H · Finish: BK



◀ **9864BK HANGING LANTERN** · Black
8"W x 19.50"H · Canopy: 5"W x 1"H · 3 – 60
Watt E12 Candelabra · Clear Glass · Finish: BK
6' Chain; 10' Wire · Damp Rated

▶ **9868BK HANGING LANTERN** · Black
6.50"W x 16.50"H · Canopy: 5"W x 1"H
1 – 100 Watt E26 Medium · Clear Glass
Finish: BK · 6' Chain; 10' Wire
Damp Rated



▶ **9466OB POST LANTERN** · *Old Bronze*
12"W x 23.50"H · 3 – 60 Watt E12 Candelabra
Antique Glass · Finish: OB · Wet Rated Fits
3" Post (sold separately)

▶ **9805OB POST** · *Old Bronze*
3"W x 83"H · Finish: OB



▲ **9465OB HANGING LANTERN** · *Old Bronze*
12"W x 22.50"H · Canopy: 5"W x 1"H · 3 – 40 Watt
E12 Candelabra · Antique Glass · Finish: OB
10' Chain; 15' Wire · Damp Rated





◀ **9461OB WALL LANTERN** · *Old Bronze*
 8"W x 18"H x 9.50"E · Backplate:
 5.50"W x 8.25"H x .75"E · Ctr/Top: 9.50"
 Ctr/Bottom: 8.50" · 1 – 75 Watt E26 Medium
 Antique Glass · Finish: OB · Wet Rated



▶ **9460OB SCONCE** · *Old Bronze*
 10"W x 14"H x 4"E · Backplate:
 8.75"W x 9"H x .50"E · Ctr/Top: 8"
 Ctr/Bottom: 6" · 2 – 40 Watt E12
 Candelabra · Antique Glass · Finish: OB
 Wet Rated · **ADA**



◀ **9463OB WALL LANTERN** · *Old Bronze*
 12"W x 26.50"H x 13.50"E · Backplate:
 5.50"W x 8.25"H x .75"E · Ctr/Top: 13.50"
 Ctr/Bottom: 13" · 3 – 60 Watt E12 Candelabra
 Antique Glass · Finish: OB · Wet Rated



▶ **9462OB WALL LANTERN** · *Old Bronze*
 10"W x 22"H x 11.50"E · Backplate:
 5.50"W x 8.25"H x .75"E · Ctr/Top: 11.50"
 Ctr/Bottom: 10.50" · 2 – 60 Watt E12
 Candelabra · Antique Glass · Finish:
 OB · Wet Rated



▶ **918142OB HANGING LANTERN** · *Old Bronze*
 12.75"W x 22.50"H · Canopy: 5"W x 1"H
 4 – 60 Watt E12 Candelabra · Clear Seeded Glass
 Finish: OB · 10' Chain; 15' Wire · Damp Rated

◀ **918141OB WALL LANTERN** · *Old Bronze*
 12.75"W x 24.50"H x 14.75"E · Backplate:
 6.50"W x 15"H x 1.25"E · Ctr/Top: 7.50"
 Ctr/Btm: 17" · 4 – 60 Watt E12 Candelabra
 Clear Seeded Glass · Finish: OB · Wet Rated



▼ **918111OB WALL LANTERN** · *Old Bronze*
 7.50"W x 17.25"H x 9.50"E · Backplate:
 6"W x 10.50"H x 1"E · Ctr/Top: 5.25"
 Ctr/Btm: 12" · 1 – 60 Watt E26 Medium
 Clear Seeded Glass · Finish: OB · Wet Rated



▲ **918121OB WALL LANTERN** · *Old Bronze*
 9.50"W x 20"H x 11.25"E · Backplate:
 6.50"W x 13"H x 1.25"E · Ctr/Top: 6.50"
 Ctr/Btm: 13.50" · 2 – 60 Watt E12 Candelabra
 Clear Seeded Glass · Finish: OB · Wet Rated



◀ **918143OB POST LANTERN** · *Old Bronze*
 12.75"W x 24.50"H · 4 – 60 Watt E12
 Candelabra · Clear Seeded Glass · Finish: OB
 Wet Rated · Fits 3" Post (sold separately)

◀ **9805OB POST** · *Old Bronze*
 3"W x 83"H · Finish: OB

grant park LED | IN OLD BRONZE



◀ 918142OB-LD HANGING LANTERN

Old Bronze • 12.75"W x 22.50"H • Canopy:
5"W x 1"H • Lumens: 1350 • Color Temperature:
3000K • CRI > 80 • Volts/Wattage: 120V 50/60
HZ/25W • Clear Seeded Glass • Finish: OB • 10'
Chain; 15' Wire Damp Rated • [LED]

▶ 918111OB-LD WALL LANTERN

Old Bronze • 7.50"W x 17.25"H x 9.50"E
Backplate: 6"W x 10.50"H x 1"E • Ctr/Top:
5.25" • Ctr/Btm: 12" • Lumens: 900 Color
Temperature: 3000K • CRI > 80
Volts/Wattage: 120V 50/60 HZ/10W
Clear Seeded Glass • Finish: OB • Wet Rated •
[LED]



▼ 918121OB-LD WALL LANTERN • *Old Bronze*

9.50"W x 20"H x 11.25"E • Backplate:
6.50"W x 13"H x 1.25"E • Ctr/Top: 6.5"
Ctr/Btm: 17.25" • Lumens: 900 • Color
Temperature: 3000K • CRI > 80 • Volts/Wattage:
120V 50/60 HZ/10W • Clear Seeded Glass • Finish: OB
Wet Rated • [LED]

◀ 918141OB-LD WALL LANTERN • *Old Bronze*

12.75"W x 24.50"H x 14.75"E • Backplate:
6.50"W x 15"H x 1.25"E • Ctr/Top: 7.5"
Ctr/Btm: 13.50" • Lumens: 1350 • Color
Temperature: 3000K • CRI > 80 • Volts/Wattage: 120V
50/60 HZ/25W • Clear Seeded Glass • Finish: OB
Wet Rated • [LED]

**Dimmable – LED
Dimmer Recommended**



▶ **9636GR HANGING LANTERN** · *Graphite*

10.50"W x 19.50"H · Canopy: 5"W x 1"H
 1 – 75 Watt E26 Medium · Clear Seeded Glass
 Finishes: GR, OB · 10' Chain; 15' Wire
 Damp Rated



▲ **9632GR WALL LANTERN** · *Graphite*

8.50"W x 16"H x 11"E · Backplate:
 5"W x 6.50"H x 1"E · Ctr/Top: 7"
 Ctr/Btm: 9" · 1 – 75 Watt E26 Medium
 Clear Seeded Glass · Finishes: GR, OB · Wet Rated



◀ **9633GR WALL LANTERN** · *Graphite*

10.50"W x 19.25"H x 13.25"E · Backplate:
 5"W x 8.75"H x 1"E · Ctr/Top: 8.25"
 Ctr/Btm: 11" · 1 – 75 Watt E26 Medium
 Clear Seeded Glass · Finishes: GR, OB · Wet Rated

▶ **9635GR POST LANTERN** · *Graphite*

10.50"W x 19.50"H · 1 – 75 Watt E26 Medium
 Clear Seeded Glass · Finishes: GR, OB · Wet Rated
 Fits 3" Post (sold separately)

▶ **9805BK POST** · *Black*

3"W x 83"H · Finish: BK

▶ **9631GR WALL LANTERN** · *Graphite*

6.50"W x 12.50"H x 8.50"E · Backplate:
 5"W x 6.50"H x 1"E · Ctr/Top: 5.25"
 Ctr/Btm: 7.25" · 1 – 75 Watt E26 Medium
 Clear Seeded Glass · Finishes: GR, OB
 Wet Rated



▼ **9633OB WALL LANTERN** · *Old Bronze*

10.50"W x 19.25"H x 13.25"E · Backplate:
5"W x 8.75"H x 1"E · Ctr/Top: 8.25"
Ctr/Btm: 11" · 1 – 75 Watt E26 Medium
Clear Seeded Glass · Finishes: GR, OB · Wet Rated



◀ **9636OB HANGING LANTERN** · *Old Bronze*

10.50"W x 19.50"H · Canopy: 5"W x 1"H
1 – 75 Watt E26 Medium · Clear Seeded Glass
Finishes: GR, OB · 10' Chain; 15' Wire · Damp Rated



▲ **9632OB WALL LANTERN** · *Old Bronze*

8.50"W x 16"H x 11"E · Backplate:
5"W x 6.50"H x 1"E · Ctr/Top: 7"
Ctr/Btm: 9" · 1 – 75 Watt E26 Medium
Clear Seeded Glass · Finishes: GR, OB · Wet
Rated



▲ **9631OB WALL LANTERN**

Old Bronze · 6.50"W x 12.50"H x 8.50"E
Backplate: 5"W x 6.50"H x 1"E
Ctr/Top: 5.25" Ctr/Btm: 7.25" · 1 – 75
Watt E26 Medium · Clear Seeded Glass
Finishes: GR, OB · Wet Rated

◀ **9635OB POST LANTERN** · *Old Bronze*

10.50"W x 19.50"H · 1 – 75 Watt E26 Medium
Clear Seeded Glass · Finishes: GR, OB · Wet
Rated · Fits 3" Post (sold separately)



◀ **9805OB POST** · *Old Bronze*

3"W x 83"H · Finish: OB



inman
park
collection

IN OLD BRONZE

▶ **9383OB WALL LANTERN** • *Old Bronze*
13"W x 32.50"H x 14"E • Backplate:
7.50"W x 15.50"H x 1.50"E • Ctr/Top: 11.75"
Ctr/Btm: 21" • 3 – 60 Watt E12 Candelabra
Antique Glass • Finish: OB • Wet Rated



◀ **9380OB WALL LANTERN**
Old Bronze • 9"W x 14.50"H x 9"E
Backplate: 5.25"W x 11"H x 1"E
Ctr/Top: 4.25" Ctr/Btm: 10.25"
2 – 60 Watt E12 Candelabra • Antique
Glass • Finish: OB • Wet Rated



◀ **9387OB POST LANTERN** • *Old Bronze*
13"W x 28"H • 3 – 60 Watt E12 Candelabra
Antique Glass • Finish: OB • Wet Rated
Fits 3" Post (sold separately)

◀ **9805OB POST** • *Old Bronze*
3"W x 83"H • Finish: OB



▶ **9386OB HANGING LANTERN** · *Old Bronze*
13"W x 26"H · Canopy: 5"W x 1"H · 3 – 40 Watt E12
Candelabra · Antique Glass · Finish: OB · 10' Chain;
15' Wire · Damp Rated



▼ **9381OB WALL LANTERN** · *Old Bronze*
9"W x 22"H x 9.50"E · Backplate:
5.25"W x 11"H x 1"E · Ctr/Top: 7.75"
Ctr/Btm: 14.25" · 2 – 60 Watt E12 Candelabra
Antique Glass · Finish: OB · Wet Rated



◀ **9382OB WALL LANTERN** · *Old Bronze*
11"W x 27"H x 12"E · Backplate:
6.50"W x 13.25"H x 1.25"E · Ctr/Top: 10"
Ctr/Btm: 17" · 3 – 60 Watt E12 Candelabra
Antique Glass · Finish: OB · Wet Rated





◀ **9885OB HANGING LANTERN** · *Old Bronze*
 8"W x 17.25"H x 6"E · Canopy: 5"W x 1"H · 1 – 100
 Watt E26 Medium · Frosted Glass · Finish: OB · 10'
 Chain; 15' Wire · Damp Rated

▶ **9882OB WALL LANTERN** · *Old Bronze*
 8"W x 16"H x 6.75"E · Backplate:
 7"W x 16"H x .50"E · Ctr/Top: 8" Ctr/Btm: 8"
 1 – 100 Watt E26 Medium · Frosted Glass
 Finish: OB · Wet Rated



◀ **9883OB WALL LANTERN** · *Old Bronze*
 9.50"W x 19"H x 8"E · Backplate:
 8.25"W x 19"H x .50"E · Ctr/Top: 9.50"
 Ctr/Btm: 9.50" · 1 – 100 Watt E26 Medium
 Frosted Glass · Finish: OB · Wet Rated

▶ **9881OB WALL LANTERN** · *Old Bronze*
 6.50"W x 13"H x 6.25"E · Backplate:
 5.50"W x 13"H x .50"E · Ctr/Top: 6.50"
 Ctr/Btm: 6.50" · 1 – 60 Watt E26 Medium
 Frosted Glass · Finish: OB · Wet Rated





◀ **917832OB HANGING LANTERN**
Old Bronze · 10.50"W x 17.25"H · Canopy:
5"W x 1"H · 3 – 60 Watt E12 Candelabra
Antique Glass · Finish: OB · 10' Chain;
15' Wire · Damp Rated



▶ **917841OB WALL LANTERN**
Old Bronze · 12.75"W x 21"H x 14.25"E
Backplate: 7.25"W x 10.75"H x 1.50"E
Ctr/Top: 5.50" · 4 – 60 Watt E12 Candelabra
Antique Glass · Finish: OB · Wet Rated



▶ **917833OB POST LANTERN**
Old Bronze · 10.50"W x 18.25"H · 3 – 60
Watt E12 Candelabra · Antique Glass
Finish: OB · Wet Rated · Fits 3" Post
(sold separately)

▶ **9805OB POST** · *Old Bronze*
3"W x 83"H · Finish: OB



▲ **917831OB WALL LANTERN** · *Old Bronze*
10.50"W x 16.25"H x 11.25"E · Backplate:
5.75"W x 8.50"H x 1.25"E · Ctr/Top: 4.25"
3 – 60 Watt E12 Candelabra · Antique Glass
Finish: OB · Wet Rated



RESPECT THE NIGHT By casting light downward toward the intended pathway or doorway, these specially designed lighting fixtures help reduce light pollution, sky glow and glare. So stars in the night sky are easier to see.



◀ **917832OB-LD HANGING LANTERN** • *Old Bronze*

10.50"W x 17.25"H • Canopy: 5"W x 1"H • Lumens: 900
Color Temperature: 3000K • CRI > 80 • Volts/Wattage:
120V 50/60 HZ/10W • Antique Glass • Finish: OB • 10'
Chain; 15' Wire • Damp Rated [LED]



▲ **917831OB-LD WALL LANTERN** • *Old Bronze*

10.50"W x 16.25"H x 11.25"E • Backplate:
5.75"W x 8.50"H x 1.25"E • Ctr/Top: 4.25" • 1 – 10
Watt LED on Board • Lumens: 900 • Color
Temperature: 3000K • CRI > 80 • Volts/Wattage: 120V
50/60 HZ/10W • Antique Glass • Finish: OB Wet
Rated • [LED]



▶ **917841OB-LD WALL LANTERN** • *Old Bronze*

12.75"W x 21"H x 14.25"E • Backplate:
7.25"W x 10.75"H x 1.50"E • Ctr/Top: 5.50"
Lumens: 1350 • Color Temperature: 3000K
CRI > 80 • Volts/Wattage: 120V 50/60 HZ/15W
Antique Glass • Finish: OB • Wet Rated • [LED]



**Dimmable – LED
Dimmer Recommended**



◀ **9837BK POST LANTERN** · Black
9.50"W x 24"H · 3 – 60 Watt E12 Candelabra
Antique Glass · Finishes: BK, OB
Wet Rated · Fits 3" Post (sold separately)

◀ **9805BK POST** · Black
3"W x 83"H · Finish: BK

▶ **9836BK HANGING LANTERN** · Black
9.50"W x 15.50"H · Canopy: 5"W x 1"H
3 – 40 Watt E12 Candelabra · Antique Glass
Finishes: BK, OB · 3' Chain; 10' Wire
Damp Rated

▶ **9832BK WALL LANTERN** · Black
6.50"W x 12"H x 8"E · Backplate:
5.25"W x 7.25"H x 1"E · Ctr/Top: 3"
Ctr/Btm: 9" · 1 – 100 Watt E26 Medium
Antique Glass · Finishes: BK, OB
Wet Rated



◀ **9831BK WALL LANTERN** · Black
5"W x 9.50"H x 6.25"E · Backplate:
4.50"W x 4.50"H x 1"E · Ctr/Top: 2"
Ctr/Btm: 7.50" · 1 – 75 Watt E26 Medium
Antique Glass · Finishes: BK, OB · Wet Rated



▲ **9834BK WALL LANTERN** · Black
9.50"W x 19"H x 10"E · Backplate:
4.50"W x 7"H x 1"E · Ctr/Top: 4" Ctr/Btm: 15"
3 – 60 Watt E12 Candelabra · Antique Glass
Finishes: BK, OB · Wet Rated



◀ **9838BK WALL LANTERN** · Black
12.50"W x 25.50"H x 13.75"E · Backplate:
4.50"W x 9.50"H x 1"E · Ctr/Top: 5" Ctr/Btm:
20.50" · 3 – 60 Watt E12 Candelabra · Antique
Glass · Finishes: BK, OB · Wet Rated



▶ **9833BK WALL LANTERN** · Black
9.25"W x 16"H x 9.25"E · Backplate:
4.50"W x 7"H x 1"E · Ctr/Top: 4" Ctr/Btm:
12" · 1 – 100 Watt E26 Medium · Antique
Glass · Finishes: BK, OB · Wet Rated

◀ **9837OB POST LANTERN** · *Old Bronze*
9.50"W x 24"H · 3 – 60 Watt E12 Candelabra
Antique Glass · Finishes: BK, OB · Wet Rated
Fits 3" Post (sold separately)

◀ **9805OB POST** · *Old Bronze*
3"W x 83"H · Finish: OB



▲ **9836OB HANGING LANTERN** · *Old Bronze*
9.50"W x 15.50"H · Canopy: 5"W x 1"H
3 – 40 Watt E12 Candelabra · Antique Glass
Finishes: BK, OB · 3' Chain; 10' Wire
Damp Rated



◀ **9832OB WALL LANTERN** · *Old Bronze*
6.50"W x 12"H x 8"E · Backplate:
5.25"W x 7.25"H x 1"E · Ctr/Top: 3"
Ctr/Btm: 9" · 1 – 100 Watt E26 Medium
Antique Glass · Finishes: BK, OB
Wet Rated

▶ **9831OB WALL LANTERN** · *Old Bronze*
5"W x 9.50"H x 6.25"E · Backplate:
4.50"W x 4.50"H x 1"E · Ctr/Top: 2"
Ctr/Btm: 7.50" · 1 – 75 Watt E26 Medium
Antique Glass · Finishes: BK, OB
Wet Rated



► **9838OB WALL LANTERN**

Old Bronze • 12.50"W x 25.50"H x 13.75"E
Backplate: 4.50"W x 9.50"H x 1"E
Ctr/Top: 5" Ctr/Btm: 20.50" • 3 – 60 Watt
E12 Candelabra • Antique Glass • Finishes:
BK, OB • Wet Rated



◄ **9834OB WALL LANTERN** • *Old Bronze*

9.50"W x 19"H x 10"E • Backplate:
4.50"W x 7"H x 1"E • Ctr/Top: 4" Ctr/Btm: 15"
3 – 60 Watt E12 Candelabra • Antique Glass
Finishes: BK, OB • Wet Rated



► **9833OB WALL LANTERN** • *Old Bronze*

8"W x 16"H x 9.25"E • Backplate:
4.50"W x 7"H x 1"E • Ctr/Top: 4" Ctr/Btm:
12" • 1 – 100 Watt E26 Medium • Antique
Glass • Finishes: BK, OB • Wet Rated

mission hills | IN BURNISHED BRONZE

▶ **9954BB HANGING LANTERN** · *Burnished Bronze*
11"W x 19"H · Canopy: 5"W x 1"H · 3 – 60 Watt E12
Candelabra · Clear Seeded Glass · Finish: BB
10' Chain; 15' Wire · Damp Rated



▼ **9955BB POST LANTERN** · *Burnished Bronze*
11"W x 19"H · 3 – 60 Watt E12 Candelabra
Clear Seeded Glass · Finish: BB · Wet Rated
Fits 3" Post (sold separately)

▼ **9805BB POST** · *Burnished Bronze*
3"W x 83"H · Finish: BB



▲ **9956BB CEILING** · *Burnished Bronze*
10.50"W x 6"H · 3 – 60 Watt E12 Candelabra
Clear Seeded Glass · Finish: BB · Damp Rated



◀ **9953BB WALL LANTERN** • *Burnished Bronze*
11"W x 20.25"H x 12.25"E • Backplate:
5.50"W x 14"H x 1.25"E • Ctr/Top: 7" Ctr/Btm: 13.25"
3 – 60 Watt E12 Candelabra • Clear Seeded Glass • Finish: BB
Wet Rated



▲ **9952BB WALL LANTERN** • *Burnished Bronze*
9"W x 16.50"H x 10.25"E • Backplate:
5"W x 11.50"H x 1.25"E • Ctr/Top: 5.75" Ctr/Btm:
10.75" 2 – 60 Watt E12 Candelabra • Clear Seeded Glass
Finish: BB • Wet Rated



◀ **9951BB WALL LANTERN** • *Burnished Bronze*
7"W x 13"H x 8.25"E • Backplate:
4.75"W x 9"H x 1.25"E • Ctr/Top: 4.50"
Ctr/Btm: 8.50" • 1 – 100 Watt E26 Medium
Clear Seeded Glass • Finish: BB • Wet Rate



◀ **9912OB WALL LANTERN**

Old Bronze · 9"W x 15.25"H x 10.25"E
Backplate: 6"W x 11.50"H x 1.25"E
Ctr/Top: 5.75" Ctr/Btm: 9.50" · 3 – 60
Watt E12 Candelabra · Antique Glass
Finish: OB · Wet Rated



▶ **9918OB WALL LANTERN**

Old Bronze · 13.25"W x 26.50"H x 14.50"E
Backplate: 6.50"W x 15.75"H x 1"E · Ctr/
Top: 8" · Ctr/Btm: 18.50" · 4 – 60 Watt E12
Candelabra · Antique Glass · Finish: OB
Wet Rated



▲ **9913OB WALL LANTERN** · *Old Bronze*

11"W x 18.50"H x 12.50"E · Backplate:
6"W x 14.25"H x 1.25"E · Ctr/Top: 7"
Ctr/Btm: 11.50" · 4 – 60 Watt E12 Candelabra
Antique Glass · Finish: OB · Wet Rated



▲ **9911OB WALL LANTERN** · *Old Bronze*

7"W x 11.75"H x 8.50"E · Backplate:
6"W x 9"H x 1.25"E · Ctr/Top: 4.50" Ctr/Btm:
7.25" · 1 – 100 Watt E26 Medium · Antique
Glass · Finish: OB · Wet Rated



◀ **9916OB SCONCE** • *Old Bronze*
 9"W x 14"H x 4"E • Backplate:
 6.75"W x 9.75"H x .75"E • Ctr/Top: 8.5"
 Ctr/Btm: 5.50" • 2 – 60 Watt E12 Candelabra
 Antique Glass • Finish: OB • Wet Rated



▲ **9917OB CEILING** • *Old Bronze*
 11.25"W x 6"H • 3 – 60 Watt E12 Candelabra
 Antique Glass • Finish: OB • Damp Rated



◀ **9915OB POST LANTERN**
Old Bronze • 11"W x 20.75"H
 4 – 60 Watt E12 Candelabra
 Antique Glass • Finish: OB • Wet Rated
 Fits 3" Post (sold separately)

◀ **9805OB POST** • *Old Bronze*
 3"W x 83"H • Finish: OB



▲ **9914OB HANGING LANTERN**
Old Bronze • 11"W x 18.50"H
 Canopy: 5"W x 1"H • 4 – 60 Watt
 E12 Candelabra • Antique Glass
 Finish: OB • 10' Chain; 15' Wire
 Damp Rated

▶ **9624OB HANGING LANTERN** • *Old Bronze*
14"W x 22.75"H • Canopy: 5"W x 1"H • 3 – 60
Watt E12 Candelabra • Antique Glass
Finish: OB • 3' Chain; 5' Wire • Damp Rated



▲ **9629OB WALL LANTERN** • *Old Bronze*
16"W x 35.50"H x 17.25"E • Backplate:
6"W x 13"H x 1"E • Ctr/Top: 18.25" Ctr/Btm:
17.25" • 4 – 60 Watt E12 Candelabra • Antique
Glass • Finish: OB • Wet Rated

▶ **9623OB • WALL LANTERN** • *Old Bronze*
14"W x 29.5"H x 15"E • Backplate:
5"W x 10.5"H x 1"E • Ctr/Top: 15.50"
Ctr/Btm: 14" • 3 – 60 Watt E12 Candelabra
Antique Glass • Finish: OB • Wet Rated
Door for Relamping





◀ **9622OB WALL LANTERN** • *Old Bronze*
11.75"W x 25"H x 12.50"E • Backplate:
5"W x 9"H x 1"E • Ctr/Top: 12.50" Ctr/Btm:
12.50" • 2 – 60 Watt E12 Candelabra • Antique
Glass • Finish: OB • Wet Rated



◀ **9621OB WALL LANTERN** • *Old Bronze*
9.50"W x 21.50"H x 10.75"E • Backplate:
5"W x 8"H x 1"E • Ctr/Top: 11.25"
Ctr/Btm: 10.25" • 1 – 100 Watt E26 Medium
Antique Glass • Finish: OB • Wet Rated

▶ **9625OB POST LANTERN** • *Old Bronze*
14"W x 27.50"H • 3 – 60 Watt E12 Candelabra
Antique Glass • Finish: OB • Wet Rated • Fits 3"
Post (sold separately)

▶ **9805OB POST** • *Old Bronze*
3"W x 83"H • Finish: OB



► **9116OB HANGING LANTERN** · *Old Bronze*
10.25"W x 20.75"H · Canopy: 5"W x 1"H · 3 – 40
Watt E12 Candelabra · Antique Glass · Finish: OB
10' Chain; 15' Wire · Damp Rated



◄ **9117OB POST LANTERN** · *Old Bronze*
10.25"W x 21"H · 3 – 60 Watt E12 Candelabra
Antique Glass · Finish: OB · Wet Rated · Fits 3"
Post (sold separately)

◄ **9805OB POST** · *Old Bronze*
3"W x 83"H · Finish: OB



► **9113OB WALL LANTERN** · *Old Bronze*
10"W x 22"H x 10"E · Backplate:
6.50"W x 9"H x 1"E · Ctr/Top: 8.25" Ctr/Btm:
13.75" · 3 – 60 Watt E12 Candelabra · Antique
Glass · Finish: OB · Wet Rated





◀ **9111OB WALL LANTERN** • *Old Bronze*
7"W x 15"H x 6.50"E • Backplate:
6"W x 5"H x .75"E • Ctr/Top: 5.75" Ctr/Btm:
9.25" • 1 – 100 Watt E26 Medium • Antique
Glass Finish: OB • Wet Rated



▶ **9112OB WALL LANTERN** • *Old Bronze*
8.50"W x 18.25"H x 8"E • Backplate:
5.50"W x 7.50"H x .75"E • Ctr/Top: 6.75"
Ctr/Btm: 11.50" • 2 – 60 Watt E12 Candelabra
Antique Glass • Finish: OB • Wet Rated



◀ **9115OB WALL LANTERN** • *Old Bronze*
12.50"W x 26.50"H x 12"E • Backplate:
7.25"W x 10.75"H x 1"E • Ctr/Top: 10.50"
Ctr/Btm: 16" • 4 – 60 Watt E12 Candelabra
Antique Glass • Finish: OB • Wet Rated

▶ **9443OB WALL LANTERN** · *Old Bronze*

13"W x 22.25"H x 12.50"E · Backplate:
6.50"W x 13.25"H x 1.25"E · Ctr/Top: 10.25"
Ctr/Btm: 125" · 1 – 75 Watt E26 Medium
Finish: OB · Wet Rated



▶ **9441OB WALL LANTERN** · *Old Bronze*

9"W x 15.50"H x 8.75"E · Backplate:
5.25"W x 11"H x 1"E · Ctr/Top: 7.50"
Ctr/Btm: 8" · 1 – 75 Watt E26 Medium
Finish: OB · Wet Rated



▲ **9442OB WALL LANTERN** · *Old Bronze*

11"W x 19.5"H x 10.5"E · Backplate:
5.25"W x 11"H x 1"E · Ctr/Top: 9.50" Ctr/Btm: 10"
1 – 75 Watt E26 Medium · Finish: OB · Wet Rated



RESPECT THE NIGHT By casting light downward toward the intended pathway or doorway, these specially designed lighting fixtures help reduce light pollution, sky glow and glare. So stars in the night sky are easier to see.



◀ **9446OB HANGING LANTERN** · *Old Bronze*
 11"W x 19.25"H · Canopy: 5"W x 1"H · 1 – 75 Watt
 E26 Medium · Finish: OB · 10' Chain; 15' Wire · Damp Rated



▼ **9445OB POST LANTERN** · *Old Bronze*
 11"W x 21"H · 1 – 75 Watt E26 Medium · Finish: OB
 Wet Rated · Fits 3" Post (sold separately)

▼ **9805OB POST** · *Old Bronze*
 3"W x 83"H · Finish: OB



▲ **9092BB WALL LANTERN** · *Burnished Bronze*
 10"W x 8.25"H x 11"E · Backplate:
 5.75"W x 7.50"H x 1"E · Ctr/Top: 3.50"
 Ctr/Btm: 4.75" · 1 – 100 Watt E26 Medium
 Acid-Washed Glass Lens
 Finish: BB · Wet Rated



▲ **9091BB WALL LANTERN** · *Burnished Bronze*
 8"W x 7"H x 9"E · Backplate:
 4.50"W x 6.25"H x 1"E · Ctr/Top: 3.50"
 Ctr/Btm: 3.50" · 1 – 60 Watt E26 Medium
 Acid-Washed Glass Lens · Finish: BB · Wet Rated



▶ **9642OB WALL LANTERN** • *Old Bronze*
9"W x 20.25"H x 10.50"E • Backplate:
5"W x 9"H x .75"E • Ctr/Top: 11" Ctr/Btm:
9.25" • 3 – 60 Watt E12 Candelabra • Antique
Glass • Finish: OB • Wet Rated



◀ **9643OB WALL LANTERN** • *Old Bronze*
11"W x 24.50"H x 12.75"E • Backplate:
5"W x 9"H x .75"E • Ctr/Top: 14" Ctr/Btm:
10.50" • 4 – 60 Watt E12 Candelabra • Antique
Glass • Finish: OB • Wet Rated



▶ **9641OB WALL LANTERN** • *Old Bronze*
7"W x 16"H x 8.25"E • Backplate:
5"W x 7"H x .75"E • Ctr/Top: 8.5" Ctr/Btm:
7.5" • 1 – 100 Watt E26 Medium • Antique Glass
Finish: OB • Wet Rated

► **9646OB HANGING LANTERN** • *Old Bronze*
11"W x 22.25"H • Canopy: 5.75"W x 1.25"H
4 – 60 Watt E12 Candelabra • Antique Glass
Finish: OB • 3' Chain; 5' Wire • Damp Rated



◀ **9645OB POST LANTERN** • *Old Bronze*
11"W x 22.75"H • 4 – 60 Watt E12 Candelabra
Antique Glass • Finish: OB • Wet Rated
Fits 3" Post (sold separately)

◀ **9805OB POST** • *Old Bronze*
3"W x 83"H • Finish: OB

LED outdoor | IN OLD BRONZE

▼ 918311OB-LD WALL LANTERN · Old Bronze

5.25"W x 15"H x 6.25"E · Backplate:
5"W x 15"H x .75"E · Ctr/Top: 7.5" · Lumens: 900
Color Temperature: 3000K · CRI > 80 · Volts/
Wattage: 120V 50/60 HZ/10W · Finish: OB · Wet
Rated · [LED]



▼ 918312OB-LD WALL LANTERN · Old Bronze

6.25"W x 18"H x 6.75"E · Backplate:
6.25"W x 18"H x 1"E · Ctr/Top: 9" · Lumens: 1350
Color Temperature: 3000K · CRI > 80 · Volts/
Wattage: 120V 50/60 HZ/15W · Finish: OB · Wet
Rated [LED]



▼ 918222OB-LD WALL LANTERN · Old Bronze

8.50"W x 18"H x 4"E · Backplate: 5"W x 10"H x 1"E
Ctr/Top: 9" · Lumens: 1800 · Color Temperature: 3000K
CRI > 80 Volts/Wattage: 120V 50/60 HZ/20W
White Glass · Finish: OB · Wet Rated · **ADA** · [LED]

▼ 918221OB-LD WALL LANTERN · Old Bronze

7"W x 18"H x 4"E · Backplate: 5"W x 10"H x 1"E
Ctr/Top: 9" · Lumens: 1800 · Color Temperature:
3000K · CRI > 80 · Volts/Wattage: 120V 50/60
HZ/20W · White Glass · Finish: OB · Wet Rated
ADA · [LED]



**Dimmable – LED
Dimmer Recommended**

▼ **918521OB-LD WALL LANTERN** · *Old Bronze*

8"W x 14"H x 4.25"E · Backplate:
8"W x 14"H x 3.75"E · Ctr/Top: 7" · Lumens: 1800
Color Temperature: 3000K · CRI > 80 · Volts/Wattage:
120V 50/60 HZ/20W · White Glass · Finish: OB
Wet Rated · [LED]



▲ **918411OB-LD WALL LANTERN** · *Old Bronze*

12"W x 12"H x 3.75"E · Backplate:
11.25"W x 11.25"H x .75"E · Ctr/Top: 6" · Lumens: 900
Color Temperature: 3000K · CRI > 80 · Volts/Wattage:
120V 50/60 HZ/25W · White Glass · Finish: OB
Wet Rated · ADA · [LED]

▼ **918011OB-LD WALL LANTERN** · *Old Bronze*

9"W x 13.50"H x 10.50"E · Backplate:
5"W x 8"H x 1"E · Ctr/Top: 4" · Lumens: 900
Color Temperature: 3000K · CRI > 80 · Volts/
Wattage: 120V 50/60 HZ /10W · Finish: OB · Wet
Rated · [LED]



► **917911OB-LD WALL LANTERN** · *Old Bronze*

9.50"W x 13.75"H x 10.75"E · Backplate:
5"W x 5"H x 1"E · Ctr/Top: 6" · Lumens: 900 · Color
Temperature: 3000K · CRI > 80 · Volts/Wattage:
120V 50/60 HZ/10W · Finish: OB · Wet Rated
[LED]



**Dimmable – LED
Dimmer Recommended**



RESPECT THE NIGHT By casting light downward toward the intended pathway or doorway, these specially designed lighting fixtures help reduce light pollution, sky glow and glare. So stars in the night sky are easier to see.



◀ **4562BB WALL LANTERN** · *Burnished Bronze*
 16.25"W x 13.50"H x 19"E · Backplate:
 6"W x 6"H x 1"E · Ctr/Top: 7.5" · 1 – 100 Watt
 E26 Medium · Finish: BB · Wet Rated



▲ **918011OB WALL LANTERN** · *Old Bronze*
 9"W x 13.50"H x 10.50"E · Backplate:
 5"W x 8"H x 1"E · Ctr/Top: 4" · 1 – 60 Watt E26
 Medium · Finish: OB · Wet Rated



▲ **4561BB WALL LANTERN** · *Burnished Bronze*
 10.75"W x 10.75"H x 14"E · Backplate:
 6"W x 6"H x 1"E · Ctr/Top: 5.75" · 1 – 100 Watt E26
 Medium · Finish: BB · Wet Rated



◀ **9493OB WALL LANTERN** · *Old Bronze*
 13"W x 14.50"H x 13.50"E · Backplate:
 5.50"W x 5.50"H x 1"E · Ctr/Top: 5.25"
 1 – 75 Watt E26 Medium · Finish: OB
 Wet Rated



▲ **9492OB WALL LANTERN**
Old Bronze · 9"W x 12.50"H x 9.50"E
 Backplate: 5.50"W x 5.50"H x 1"E
 Ctr/Top: 5" · 1 – 75 Watt E26 Medium
 Finish: OB · Wet Rated



▶ **9546OB CEILING** · *Old Bronze*
 11.50"W x 8.50"H · 3 – 60 Watt E12
 Candelabra · Antique Glass · Finish: OB
 Damp Rated



◀ **9541OB CEILING** · *Old Bronze*
 11"W x 10"H · 3 – 60 Watt E12
 Candelabra · Clear Seeded Glass · Finish:
 OB · Damp Rated



RESPECT THE NIGHT By casting light downward toward the intended pathway or doorway, these specially designed lighting fixtures help reduce light pollution, sky glow and glare. So stars in the night sky are easier to see.



▲ **9850BK WALL LANTERN**
Black · 5"W x 8.25"H x 6"E
 Backplate: 5"W x 5"H x 1"E
 Ctr/Top: 3" Ctr/Btm: 5.25"
 1 – 60 Watt E26 Medium · Clear
 Glass · Finishes: BK, OB
 Wet Rated



▲ **9850OB WALL LANTERN**
Old Bronze · 5"W x 8.25"H x 6"E
 Backplate: 5"W x 5"H x 1"E
 Ctr/Top: 3" Ctr/Btm: 5.25"
 1 – 60 Watt E26 Medium · Clear
 Glass · Finishes: BK, OB
 Wet Rated



▲ **9937BK CEILING**
Black · 8"W x 5"H
 1 – 60 Watt E26 Medium
 Textured Glass
 Finishes: BK, WH
 Damp Rated



▲ **9939WH CEILING**
White · 10"W x 5"H
 2 – 60 Watt E26 Medium
 Textured Glass
 Finishes: BK, WH
 Damp Rated



▲ **9830BK WALL LANTERN**
Black · 7"W x 12"H x 8"E
 Backplate: 5.25"W x 7.25"H x 1"E
 Ctr/Top: 2.75" · Ctr/Btm: 9.25"
 1 – 60 Watt E26 Medium · Clear
 Glass Finishes: BK, OB · Wet Rated



▲ **9830OB WALL LANTERN**
Old Bronze · 7"W x 12"H x 8"E
 Backplate: 5.25"W x 7.25"H x 1"E
 Ctr/Top: 2.75" · Ctr/Btm: 9.25"
 1 – 60 Watt E26 Medium · Clear
 Glass · Finishes: BK, OB · Wet Rated



▲ **9237BK CEILING**
Black · 8.50"W x 5"H
 1 – 60 Watt E26 Medium
 Textured Glass
 Finishes: BK, WH
 Damp Rated



▲ **9239WH CEILING**
White · 10.50"W x 5"H
 2 – 60 Watt E26 Medium
 Textured Glass
 Finishes: BK, WH
 Damp Rated



▲ **9800OB CEILING**
Old Bronze
 11.25"W x 5"H
 2 – 60 Watt E26 Medium
 Frosted Glass · Finishes:
 BK,OB · Damp Rated



▲ **9802OB CEILING**
Old Bronze
 11"W x 6.50"H
 3 – 60 Watt E12 Candelabra
 Clear Glass · Finishes:
 BK,OB · Damp Rated



▶ **9809OB
 PIER MOUNT**
Old Bronze
 6"W x 3.5"H
 Finishes:
 BB, BK, OB



▲ **9946BK WALL LANTERN**
Black · 4"W x 7"H x 5"E
 Backplate: 4.50"W x 4.50"H
 x 1.75"E · Ctr/Top: 2.50"
 Ctr/Btm: 4.50" · 1 – 100 Watt E26
 Medium · Clear Glass
 Finish: BK · Wet Rated



▲ **9502WH
 FLOOD LIGHT**
White
 6"W x 5"H x 5.50"E
 2 – 150 Watt E26
 Medium · Finishes:
 RZ, WH · Damp Rated



▲ **9502RZ
 FLOOD LIGHT**
Bronze
 6"W x 5"H x 5.50"E
 2 – 150 Watt E26
 Medium · Finishes:
 RZ, WH · Damp Rated



ADELE
 ▲ 4444SQ
 16.25"W x 16"H
 see page 16



ALEXANDER
 ▲ 4743BB-610
 ► 4743WG-610
 18"W x 12"H
 see page 22



ALEXANDER
 ▲ 8073BB
 ► 8073WG
 16.25"W x 7.50"H
 see page 25



ALISA
 ◀ 4486PN-159
 16.25"W x 10"H
 see page 29

ALISA
 ► 4488PN-574-CR
 20.25"W x 14.75"H
 see page 28



ALSTON
 ▼ 521044OB
 24.50"W x 17"H
 see page 32

ALSTON
 ▲ 521041OB
 14"W x 17.25"H
 see page 31



ASHER
 ▼ 214931CZ-661
 15"W x 11.50"H
 see page 38



A modern laundry room featuring white cabinetry, a large window with a view of greenery, and a ceiling light fixture. The room includes a sink, a wicker basket, and a washing machine. The text "ceiling collection" is overlaid on the image.

ceiling
collection



BARCLAY
 ◀ 3588CB
 18"W x 18.50"H
 see page 56



BELMONT
 ◀ 3418BB
 ▼ 3418BB-SW
 14.50"W x 14"H
 see page 65



BERKELEY
 ▼ 4964WG-617
 21.50"W x 19.5"H
 see page 71



BLAKELY
 ▲ 9481AS
 ► 9481CG-CR
 12.25"W x 16.75"H
 see page 80



BLAKELY
 ▲ 9481AG-CR
 12.25"W x 16.75"H

CAMILLE
 ▼ 210731SF
 15.25"W x 12.5"H
 see page 99



CARRINGTON
 ► 7023PN-CR
 22.50"W x 26"H
 see page 105



CHANDLER
 ► 3071BB
 ▼ 3071MN
 16"W x 16"H
 see page 110





CHAPMAN
◀ 3947BB-SW
17.50"W x 12"H
see page 117



CHAPMAN
▲ 3947BB-TW
17.50"W x 12"H
see page 117



CHAPMAN
▶ 3947MN-SW
17.50"W x 12"H
see page 117



CHASTAIN
▲ 4208TB
20.25"W x 19"H
see page 125



CHATEAU
▶ 4094FO
15.50"W x 21.25"H
see page 129



CITY
▲ 219281PN
19"W x 7.25"H
see page 132



CORRIGAN
▶ 210941AS-652
15"W x 16.50"H
see page 140



COVINGTON
▲ 9411AN
▶ 9411BB
11"W x 12"H
see page 144



ELLIS

- ▲ 4549BG
- ▶ 4549AS
- ▶ 4549CG

16"W x 8.50"H
see page 157

ELLIS

- ▶ 4545BG-582
- ▶ 4545AS-582
- ▼ 4545CG-582

18.25"W x 15.5"H
see page 155



FIFTH AVENUE

▲ 9173WG
14"W x 9.50"H
see page 166

▶ 4003WG-487
15"W x 12"H
see page 166



FIRE AND ICE

▲ 220841FI
18"W x 12"H
see page 170



HILL HOUSE

▲ 2273BB
13.75"W x 8"H
see page 180

◀ 3563BB
16.25"W x 16.25"H
see page 180



JACKSON
▲ 4895OR
15.75"W x 8"H
see page 191



LEIGH
◀ 4704BB
10.5"W x 18.5"H
see page 202



LOFT
▲ 3923BB-480
15.25"W x 11.25"H
see page 207



LOFT
▲ 3923MN-480
15.25"W x 11.25"H
see page 207



LOFT
▲ 3923BB-479
15.25"W x 11.25"H
see page 207



LOWELL
▲ 4795TZ
15"W x 14.50"H
see page 209

LUNA
▼ 3933WG-476
17"W x 13"H
see page 210



MARGO
▶ 4224WG-551-CR
20"W x 18"H
see page 215





MAXWELL
 ◀ 4533CB
 15.25"W x 13.75"H
 see page 216

MID-CENTURY

- ▶ 321111AD
- ▼ 321111PN

11.25"W x 15"H
 see page 222



MIDTOWN
 ▶ 2015PN-480
 15.75"W x 7.25"H
 see page 231



MIDTOWN
 ▶ 2015BB-479
 15.75"W x 7.25"H
 see page 231



MIDTOWN
 ◀ 2015BB-480
 15.75"W x 7.25"H
 see page 231



MIDTOWN
 ◀ 2015MN-480
 15.75"W x 7.25"H
 see page 231

MIDTOWN
 ▶ 3914PN-459
 17"W x 13"H
 see page 231



MIDTOWN
 ▶ 3914BB-459
 17"W x 13"H
 see page 230



MIDTOWN
 ◀ 3914BB-458
 17"W x 13"H
 see page 231



MIDTOWN
 ◀ 3914MN-459
 17"W x 13"H
 see page 230



MORGAN
◀ 7001BB
▶ 7001PN
12"W x 21.75"H
see page 245



REID
▲ 212031RT
14.25"W x 7.25"H
see page 279

REID
▶ 212041RT
14.25"W x 19"H
see page 278



NASH
▲ 213211GM-LD
16"W x 4.50"H
see page 247

Dimmable – LED
Dimmer Recommended

REGAN
▶ 219441CG
15"W x 10.75"H
see page 276





RIVER CREST
▲ 3603RI
18"W x 19"H
see page 289



RIVER CREST
▼ 2283RI
13"W x 8"H
see page 288



RIVER CREST
▲ 2287RI
24"W x 10.50"H
see page 286

SINCLAIR
▶ 517441RB
18"W x 15.75"H
see page 302



STANTON
▲ 4037BB
▶ 4037BN
▶ 4037BB-SW
17"W x 10"H
see page 307

STANTON
▲ 4032BN-236
▶ 4032BB-236
7.25"W x 11"H
see page 308





STUDIO
◀ 2305PN-513
15.75"W x 7.25"H
see page 316



STUDIO
◀ 3874PN-496
15"W x 11"H
see page 316



TAYLOR
◀ 4594PN-592
▼ 4594BB-605
24"W x 23"H
see page 321



TAYLOR
▲ 4593PN-594
▶ 4593BB-607
12"W x 16.25"H
see page 321



WEST PORT
▶ 520141OB
12"W x 17.75"H
see page 326



WYATT
◀ 9001SY
13.50"W x 17.50"H
see page 340



WYATT
◀ 2067SY
16.50"W x 6.50"H
see page 338



WYATT
◀ 4253SY
16.50"W x 13.50"H
see page 338



▲ 3537CH-134
Chrome
 ▲ 3537BB-134
Burnished Bronze
 ◀ 3537PN-134
Polished Nickel
 10.5"W x 9.25"H
 Canopy: 5"W x 1"E
 1 – 75 Watt Medium
 Clear Glass
 Finishes: BB, CH, PN



▲ 3537CH-129
Chrome
 ▲ 3537BB-129
Burnished Bronze
 ◀ 3537PN-129
Polished Nickel
 10.50"W x 9"H
 Canopy: 5"W x 1.25"H
 1 – 75 Watt E26 Medium
 Milk Glass
 Finishes: BB, CH, PN



▲ 3533CH-129
Chrome
 ▲ 3533BB-129
Burnished Bronze
 ▶ 3533PN-129
Polished Nickel
 10.50"W x 11.50"H
 Canopy: 5"W x 1.25"H
 1 – 75 Watt E26 Medium
 Milk Glass
 Finishes: BB, CH, PN




▲ 3533AD-134
Aged Brass
 ▲ 3533CH-134
Chrome
 ◀ 3533PN-134
Polished Nickel
 ◀ 3533BB-134
Burnished Bronze
 10.50"W x 11.50"H
 Canopy: 5"W x 1.25"H
 1 – 75 Watt E26 Medium
 Clear Glass
 Finishes: AD, BB, CH, PN



▶ **4859GR**

Graphite
15.75"W x 8"H
3 – 100 Watt E26 Medium
Frosted Glass Diffuser
Finish: GR
Damp Rated



◀ **214141PN**

Polished Nickel
13"W x 12.75"H
4 – 60 Watt E12 Candelabra
Clear Glass
Finishes: AD, BB, BN, PN
Damp Rated



▶ **214141BN**

Brushed Nickel
13"W x 12.75"H
4 – 60 Watt E12 Candelabra
Clear Glass
Finishes: AD, BB, BN, PN
Damp Rated



◀ **214031BN**

Brushed Nickel
11.50"W x 13.75"H
3 – 60 Watt E12 Candelabra
Clear Seeded Glass
Finishes: BB, BN, PN
Damp Rated



◀ **214141BB**

Burnished Bronze
13"W x 12.75"H
4 – 60 Watt E12 Candelabra
Clear Glass
Finishes: AD, BB, BN, PN
Damp Rated

▶ **214031PN**

Polished Nickel
11.50"W x 13.75"H
3 – 60 Watt E12 Candelabra
Clear Seeded Glass
Finishes: BB, BN, PN
Damp Rated



◀ **214031BB**

Burnished Bronze
11.50"W x 13.75"H
3 – 60 Watt E12 Candelabra
Clear Seeded Glass
Finishes: BB, BN, PN
Damp Rated

▶ **214141AD**

Aged Brass
13"W x 12.75"H
4 – 60 Watt Candelabra
Clear Glass
Finishes: AD, BB, BN, PN
Damp Rated





- ◀ **219031BZ**
Bronze
- ◀ **219031CH**
Chrome
- ◀ **219031MN**
Matte Nickel
- ◀ **219031MW**
White

14.75"W x 5.25"H
3 – 60 Watt E26 Medium
White Alabaster Glass
Finishes: BZ, CH, MN, MW

- ▶ **219022BZ**
Bronze
- ▶ **219022CH**
Chrome
- ▶ **219022MN**
Matte Nickel
- ▶ **219022MW**
White

13"W x 5.25"H
2 – 60 Watt E26 Medium
White Alabaster Glass
Finishes: BZ, CH, MN, MW



- ▲ **219121BZ**
Bronze
11"W x 4.50"H

219122BZ **219131BZ**
13"W x 5.25"H 14.75"W x 5.25"H

2 – 60 Watt E26 Medium
Mist Scavo Glass
Finish: BZ



- ◀ **219021BZ**
Bronze
- ◀ **219021CH**
Chrome
- ◀ **219021MN**
Matte Nickel
- ◀ **219021MW**
White

11"W x 4.50"H
2 – 60 Watt E26 Medium
White Alabaster Glass
Finishes: BZ, CH, MN, MW



◀ 214721MN

Matte Nickel

◀ 214721BZ

Bronze

◀ 214721CH

Chrome

◀ 214721BN

Brushed Nickel

11"W x 4.50"H

2 – 60 Watt E26 Medium

Soft White Glass

Finishes: BN, BZ, CH, MN

▶ 214722MN

Matte Nickel

▶ 214722BZ

Bronze

▶ 214722CH

Chrome

▶ 214722BN

Brushed Nickel

13"W x 5.25"H

2 – 60 Watt E26 Medium

Soft White Glass

Finishes: BN, BZ, CH, MN



◀ 214731MN

Matte Nickel

◀ 214731BZ

Bronze

◀ 214731CH

Chrome

◀ 214731BN

Brushed Nickel

14.75"W x 5.25"H

3 – 60 Watt E26 Medium

Soft White Glass

Finishes: BN, BZ, CH, MN





▲ **2826FF-SW**
Soft White Glass
Finishes: BB, BN, MN Clips
Damp Rated

2826FF-SW
16"W x 5"H
3 – 60 Watt E26 Medium



▲ **2826FF-AL**
White Faux Alabaster Glass
Finishes: MBZ, MN, MW Clips
Damp Rated

2826FF-AL
16"W x 5"H
3 – 60 Watt E26 Medium



▲ **2826FF-MS**
Mist Scavo Glass
Finishes: MBZ, MN, MW
Damp Rated

2826FF-MS
16"W x 5"H
3 – 60 Watt E26 Medium

2822FF-SW
12"W x 3.75"H
2 – 60 Watt E26
Medium

2820FF-SW
20"W x 5.5"H
4 – 60 Watt E26
Medium

2822FF-AL
12"W x 3.75"H
2 – 60 Watt E26
Medium

2820FF-AL
20"W x 5.50"H
4 – 60 Watt E26
Medium

2822FF-MS
12"W x 3.75"H
2 – 60 Watt E26
Medium

2820FF-MS
20"W x 6"H
4 – 60 Watt E26
Medium



▼ **4453BG-561**
Brushed Gold
18"W x 8.25"H
Canopy: 4.75"W x .75"H .
4 – 60 Watt E26 Medium
Decorative White
Fabric Shade
Frosted Glass Diffuser
Finish: BG

▼ **5569WH**
White
6"W x 7"H
1 – 60 Watt E26 Medium
White Glass
Damp Rated
Finishes: MN, WH

▲ **4452BG-557**
Brushed Gold
12"W x 7.25"H
Canopy: 4.75"W x .75"H
2 – 60 Watt E26 Medium
Decorative White
Fabric Shade
Frosted Glass Diffuser
Finish: BG





▲ **2323SA-SW**
Sable
12.50"W x 4.50"H
2 – 60 Watt E26 Medium

▲ **2325SA-SW**
Sable
14.75"W x 5.25"H
3 – 60 Watt E26 Medium

Soft White Glass
Finishes: AD, AN, BB, CG,
MN, PN, SA, WG



▲ **2323PN-SW**
Polished Nickel
12.50"W x 4.50"H
2 – 60 Watt E26 Medium

▲ **2325PN-SW**
Polished Nickel
14.75"W x 5.25"H
3 – 60 Watt E26 Medium

Soft White Glass
Finishes: AD, AN, BB, CG,
MN, PN, SA, WG



▲ **2323AD-SW**
Burnished Bronze
12.50"W x 4.50"H
2 – 60 Watt E26 Medium

▲ **2325AD-SW**
Burnished Bronze
14.75"W x 5.25"H
3 – 60 Watt E26 Medium

Soft White Glass
Finishes: AD, AN, BB, CG,
MN, PN, SA, WG



▲ **2323CG-SW**
Capital Gold
12.50"W x 4.50"H
2 – 60 Watt E26 Medium

▲ **2325CG-SW**
Capital Gold
14.75"W x 5.25"H
3 – 60 Watt E26 Medium

Soft White Glass
Finishes: AD, AN, BB, CG,
MN, PN, SA, WG



▲ **2323AN-SW**
Antique Nickel
12.50"W x 4.50"H
2 – 60 Watt E26 Medium

▲ **2325AN-SW**
Antique Nickel
14.75"W x 5.25"H
3 – 60 Watt E26 Medium

Soft White Glass
Finishes: AD, AN, BB, CG,
MN, PN, SA, WG



▲ **2323BB-SW**
Burnished Bronze
12.50"W x 4.50"H
2 – 60 Watt E26 Medium

▲ **2325BB-SW**
Burnished Bronze
14.75"W x 5.25"H
3 – 60 Watt E26 Medium

Soft White Glass
Finishes: AD, AN, BB, CG,
MN, PN, SA, WG



▲ **2323MN-SW**
Matte Nickel
12.50"W x 4.50"H
2 – 60 Watt E26 Medium

▲ **2325MN-SW**
Matte Nickel
14.75"W x 5.25"H
3 – 60 Watt E26 Medium

Soft White Glass
Finishes: AD, AN, BB, CG,
MN, PN, SA, WG



▲ **2323WG-SW**
Winter Gold
12.50"W x 4.50"H
2 – 60 Watt E26 Medium

▲ **2325WG-SW**
Winter Gold
14.75"W x 5.25"H
3 – 60 Watt E26 Medium

Soft White Glass
Finishes: AD, AN, BB, CG,
MN, PN, SA, WG



▲ **2032MN**
Matte Nickel
White Glass
Finishes: MN, OR
Damp Rated



▲ **2032OR**
Oil Rubbed Bronze
White Glass
Finishes: MN, OR
Damp Rated



▲ **2042OR**
Oil Rubbed Bronze
Mist Scavo Glass
Finish: OR
Damp Rated

2032MN
12"W x 3.5"H
2 – 60 Watt E26
Medium

2034MN
14"W x 5"H
3 – 60 Watt E26
Medium

2032OR
12"W x 3.5"H
2 – 60 Watt E26
Medium

2034OR
14"W x 5"H
3 – 60 Watt E26
Medium

2042OR
12.50"W x 4.25"H
2 – 60 Watt E26
Medium

2044OR
14"W x 5"H
3 – 60 Watt E26
Medium



▲ **213911BB-LD**
Burnished Bronze
15"W x 4.50"H
Lumens: 2125
Temperature:
3000K, CRI>80
Volts/Watts:
120V 50/60 HZ/ 25W
Milk Glass
Finish: BB
Damp Rated
[LED]



▲ **213912BB-LD**
Burnished Bronze
15"W x 4.50"H
Lumens: 2125
Temperature:
3000K, CRI>80
Volts/Watts:
120V 50/60 HZ/ 25W
Milk Glass
Finish: BB
Damp Rated
[LED]

Dimmable – LED
Dimmer Recommended



◀ **2037OR**
Oil Rubbed Bronze
14"W x 11.75"H
Canopy: 5"W x 1.25"H
3 – 60 Watt E26 Medium
White Glass
Finishes: MN, OR
Damp Rated



◀ **2037MN**
Matte Nickel
14"W x 11.75"H
Canopy: 5"W x 1.25"H
3 – 60 Watt E26 Medium
White Glass
Finishes: MN, OR
Damp Rated



◀ **2047OR**
Oil Rubbed Bronze
14"W x 11.75"H
Canopy: 5"W x 1.25"H
3 – 60 Watt E26 Medium
Mist Scavo Glass
Finish: OR
Damp Rated



▲ **5356MN**
Matte Nickel
White Glass
Finishes: MN, WH
Damp Rated



▲ **5676BB**
Burnished Bronze
White Faux Alabaster Glass
Finishes: BB, MN
Damp Rated



▲ **5676MN**
Matte Nickel
White Faux Alabaster Glass
Finishes: BB, MN
Damp Rated



▲ **5376BB**
Burnished Bronze
Mist Scavo Glass
Finish: BB
Damp Rated

5356MN 7"W x 4.50"H 1 – 60 Watt E26 Medium	5358MN 9"W x 5.25"H 2 – 60 Watt E26 Medium	5676BB 7"W x 5"H 1 – 60 Watt E26 Medium	5678BB 9"W x 5"H 2 – 60 Watt E26 Medium	5676MN 7"W x 5"H 1 – 60 Watt E26 Medium	5678MN 9"W x 5"H 2 – 60 Watt E26 Medium	5376BB 7"W x 4"H 1 – 60 Watt E26 Medium	5378BB 9"W x 5"H 2 – 60 Watt E26 Medium
--	--	---	---	---	---	---	---



◀ **2717BB**
Burnished Bronze
15"W x 14"H
Canopy: 6"W x 2.50"H
3 – 60 Watt E26 Medium
White Faux Alabaster Glass
Finishes: BB, MN
Damp Rated

▶ **2718MN**
Matte Nickel
15.75"W x 17"H
Canopy: 5"W x 1"H
3 – 100 Watt E26
Medium
Finish: MN
Damp Rated



▶ **2747BB**
Burnished Bronze
15"W x 14"H
Canopy: 5"W x 1.50"H
3 – 60 Watt E26 Medium
Mist Scavo Glass
Finish: BB
Damp Rated



◀ **2717MN**
Matte Nickel
15"W x 14"H
Canopy: 6"W x 2.50"H
3 – 60 Watt E26 Medium
Faux White Alabaster Glass
Finishes: BB, MN
Damp Rated



◀ **9181RT**
Rustic
11.5"W x 18.5"H
3 – 60 Watt
Candelabra
Finish: RT



ABELLA
 ◀ 523042CG
 18.50"W x 28.75"H
 see page 14



ABELLA
 ▶ 523041CG
 14.25"W x 17"H
 see page 15



ALEXANDER
 ▲ 9691WG
 ▶ 9691BB
 11.75"W x 19"H
 see page 20



ALEXANDER
 ▲ 9692WG
 ▶ 9692BB
 18.25"W x 27.50"H
 see page 20



ALEXANDER
 ▲ 9693WG
 ▶ 9693BB
 24"W x 33"H
 see page 21



**521041OB
 FOYER**
 Includes
 Semi-Flush Option
 14"W x 17.25"H



ALSTON
 ▲ 521041OB
 14"W x 17"H
 ▶ 521042OB
 16"W x 27"H
 see page 31



ALSTON
 ◀ 521043OB
 22"W x 38"H
 ▼ 521044OB
 24.50"W x 16.75"H
 see page 32

**521044OB
 FOYER**
 Includes
 Semi-Flush Option
 24.50"W x 17"H





foyer
collection



ARDEN
 ◀ 511241BS-317
 15"W x 26.75"H
 see page 36



ASHER
 ▶ 514941CZ
 17"W x 29.5"H
 see page 38



AVANTI
 ▲ 517641RT-376
 15"W x 27"H
 see page 43



AVANTI
 ▲ 517642RT-376
 22"W x 38"H
 see page 43



BAILEY
 ▼ 4728WG
 15"W x 26"H
 see page 55



BAILEY
 ▲ 4727WG
 12.50"W x 14.50"H
 see page 55



BLAIR
 ◀ 9896AS
 18"W x 34"H
 see page 74

BENNETT
 ▶ 511141RS-665
 15"W x 24.25"H
 see page 68



BLAIR
 ▶ 9894AS
 12"W x 18.50"H
 see page 74



BLAKELY
 ► 9481CG-CR
 12.25"W x 17.75"H
 see page 80




BLAKELY
 ► 9481AS-CR
 ▼ 9481AG-CR
 12.25"W x 17.75"H
 see page 80


BLAKELY
 ► 9481CG
 12.25"W x 17.75"H
 see page 80



BLAKELY
 ► 9481AS
 ▼ 9481AG
 12.25"W x 17.75"H
 see page 80



9481AG-CR
 Includes Flush Mount
 Option
 12.25"W x 16.75"H
 Finishes: AG, AS, CG

9481AS
 Includes Flush Mount
 Option
 12.25"W x 16.75"H
 Finishes: AG, AS, CG




BLAKELY
 ► 9482CG-CR
 18"W x 29"H
 see page 81



BLAKELY
 ► 9482AS-CR
 ▼ 9482AG-CR
 18"W x 29"H
 see page 81



BLAKELY
 ► 9482CG
 18"W x 29"H
 see page 81



BLAKELY
 ► 9482AS
 ▼ 9482AG
 18"W x 29"H
 see page 81



BLAKELY
 ► 9483CG-CR
 22.50"W x 36.50"H
 see page 82



BLAKELY
 ► 9483AS-CR
 ▼ 9483AG-CR
 22.50"W x 36.50"H
 see page 82



BLAKELY
 ► 9483CG
 22.50"W x 36.50"H
 see page 82



BLAKELY
 ► 9483AS
 ▼ 9483AG
 22.50"W x 36.50"H
 see page 82





BODEN
 ◀ 512341BN
 ▶ 512341BB
 18.75"W x 30"H
 see page 88



CAMBRIDGE
 ▶ 513641WG
 16"W x 31"H
 see page 92



CARLYLE
 ▲ 511741GS
 15.25"W x 26.5"H
 see page 102



CELINE
 ◀ 4784AS-000
 21.75"W x 30.25"H
 see page 109



CHARLESTON
 ▲ 313342SG
 15"W x 26.50"H
 see page 121



4208TB
 Includes Flush
 Mount Option
 20.25"W x 19"H



CHASTAIN
 ▲ 4208TB
 20.25"W x 20"H
 see page 125

CHATEAU
 ▼ 9471FO
 12.50"W x 21"H
 see page 129



CHATEAU
 ▼ 9472FO
 17"W x 29.50"H
 see page 129



CHATEAU
 ▶ 9473FO
 25"W x 38"H
 see page 129




CITY
 ▶ 519241PN
 16.50"W x 29.25"H
 see page 133





COLE
▲ 521341AO
12"W x 16"H
see page 137



COLE
▲ 521342AO
15"W x 27.25"H
see page 136

COLE
▼ 521343AO
16"W x 29"H
see page 136



COLE
► 521381AO
22"W x 38"H
see page 136



COVINGTON
◀ 9401AN
16"W x 26"H
see page 142



9401BB
Includes Chain
Mount Option
16"W x 26"H
Finishes: AN, BB



COVINGTON
◀ 9401BB
16"W x 26"H
see page 142



9401BB
Includes Flush
Mount Option
11"W x 12"H



COVINGTON
▲ 9411BB
11"W x 13.50"H
see page 144



9411AN
Includes Flush
Mount Option
11"W x 12"H



COVINGTON
▲ 9411AN
11"W x 13.50"H
see page 144



DAWSON
▶ 519342AD
18"W x 26.50"H
see page 148



DAWSON
▲ 519341AD
14"W x 19"H
see page 148



FIFTH AVENUE
◀ 9083WG-484
26.25"W x 47"H
see page 164

FIFTH AVENUE
▼ 9081WG-485
8.50"W x 18.50"H
see page 164



FIFTH AVENUE
▲ 9082WG-484
19.50"W x 33.50"H
see page 164



EVERLEIGH
▶ 517741FG
16"W x 28.50"H
see page 163



EVERLEIGH
▲ 517761FG
24"W x 41.25"H
see page 163



FIRE AND ICE
◀ 520881FI
22"W x 34.75"H
see page 169



FIRE AND ICE
▲ 520841FI
17.50"W x 23.75"H
see page 171



FLYNN
◀ 511041GM-316
16"W x 26"H
see page 173



KINGSLEY
▶ 518741DS
17.75"W x 30.25"H
see page 195



KNOX
◀ 512431OB
12"W x 21"H
see page 199



KNOX
◀ 512441OB
15"W x 25.5"H
see page 199



KNOX
◀ 512462OB
20"W x 30"H
see page 199



LEIGH
◀ 4704BB
10.50"W x 19.75"H
see page 202

4704BB
Includes Flush
Mount Option
10.50"W x 18.50"H



LEIGH
▶ 4705BB
16"W x 27"H
see page 202



MANHATTAN
◀ 520661PN
22"W x 37.50"H
see page 213

MANHATTAN
▶ 520641PN
15"W x 27.50"H
see page 213





MIDTOWN
 ▲ 9046BB-463
 ▲ 9046BB-462
 ▲ 9046MN-463
 ◀ 9046PN-463
 11"W x 21.25"H
 see page 233



MIDTOWN
 ▲ 9041BB-472
 ▲ 9041BB-471
 ▲ 9041MN-472
 ◀ 9041PN-472
 14"W x 28"H
 see page 233



MIDTOWN
 ◀ 9047BB-478
 ◀ 9047BB-477
 ◀ 9047MN-478
 ◀ 9047PN-478
 11"W x 21.25"H
 see page 232

MIDTOWN

- ▶ 9042BB-474
- ▶ 9042BB-473
- ▶ 9042MN-474
- ▶ 9042PN-474

14"W x 28"H
see page 232



MILAN

- ▶ 519741CG
- 15"W x 30.50"H
see page 240



MORGAN

- ▶ 7001BB
- 12"W x 22.75"H
see page 245



MORGAN

- ▶ 7001PN
- 12"W x 22.75"H
see page 245


MORGAN

- ◀ 7002PN
 - ▶ 7002BB
- 15"W x 26.75"H
see page 245



MORGAN

- ◀ 7003PN
 - ▶ 7003BB
- 22"W x 38"H
see page 245



OLIVIA
▶ 515041WG
15"W x 28.25"H
see page 256



OLIVIA
▲ 515042WG
14.50"W x 26.50"H
see page 256

OXFORD
▶ 519641SP
16"W x 26.50"H
see page 259



PORTER
▶ 520941RB
16"W x 28"H
see page 265



RAVENWOOD
▶ 519841BI
16.25"W x 26"H
see page 270



REGAN
◀ 519442CG-417
15"W x 28"H
see page 274



REGAN
▼ 519441CG
12"W x 15.50"H
see page 274



RENAISSANCE
◀ 521531RN
12.75"W x 29"H
see page 284



RIVER CREST
◀ 9354RI
12"W x 20.50"H
see page 286



ROWAN
◀ 511641RT
16"W x 27.75"H
see page 293





SEATON
 ◀ 510842SF
 16"W x 26.50"H
 see page 298

SINCLAIR
 ▶ 517441RB
 18"W x 19"H
 see page 302



517441RB
 Includes Chain Mount Option
 18"W x 15.75"H



SEATON
 ▶ 510841SF
 14.75"W x 31"H
 see page 298



STANTON
 ◀ 4036PN
 ▶ 4036BN
 10.25"W x 17"H
 see page 309



STANTON
 ▶ 4036BB
 10.25"W x 17"H
 see page 309



STANTON
 ▶ 9552BB
 16.75"W x 29"H
 see page 309



STANTON
 ▶ 9552PN
 16.75"W x 29"H
 see page 309



STANTON
 ▶ 9552BN
 16.75"W x 29"H
 see page 309



STANTON
▶ 9553BB
22"W x 35.50"H
see page 308



STANTON
▶ 9553PN
22"W x 35.50"H
see page 308



STANTON
▶ 9553BN
22"W x 35.50"H
see page 308



STANTON
▲ 4032BN-236
7.25"W x 11"H
see page 308

4032BN-236
FOYER
Includes Chain
Mount Option
7.25"W x 11"H



STANTON
▲ 4032BB-236
7.25"W x 11"H
see page 308

4032BB-236
FOYER
Includes Chain
Mount Option
7.25"W x 11"H



VINEYARD
▶ 510342FC
15"W x 28"H
see page 323



VINEYARD
▶ 510341FC
17.25"W x 29"H
see page 323





WEST PORT
▲ 520141OB
12"W x 14.25"H
see page 326



520141OB
SEMI-FLUSH
Includes Flush
Mount Option
12"W x 17.75"H



WEST PORT
▶ 520181OB
22"W x 37.75"H
see page 327

WEST PORT
◀ 520142OB
16"W x 26.50"H
see page 327



WESTBROOK
▲ 510141WG
▶ 510141BB
12"W x 14.75"H
see page 328



WESTBROOK
◀ 510161WG
▶ 510161BB
16"W x 26.75"H
see page 329



WINDSOR
◀ 513841SF
15.75"W x 29.50"H
see page 333



WINDSOR
◀ 513842SF
16"W x 25.50"H
see page 333



WRIGHT
 ◀ 520441PN
 12"W x 18"H
 see page 335



WRIGHT
 ◀ 520443PN
 15"W x 27"H
 see page 335



WRIGHT
 ◀ 520442PN
 15"W x 28.50"H
 see page 335



WYATT
 ▶ 9003SY
 30"W x 45.50"H
 see page 342



WYATT
 ◀ 9002SY
 24"W x 38.50"H
 see page 342



9001SY
 Includes Flush
 Mount Option
 13.50"W x 17.50"H

WYATT
 ▶ 9001SY
 13.50"W x 18"H
 see page 342



ZANDER
 ▼ 521981AD
 16"W x 26"H
 see page 345





◀ **522381BN**
Brushed Nickel

◀ **522381PN**
Polished Nickel

▶ **522381BB**
Burnished Bronze

17"W x 34.50"H

Canopy: 5"W x 0.75"H

8 – 60 Watt E12 Candelabra

Finishes: BB, BN, PN

10' Chain; 15' Wire



▶ **511441PN**
Polished Nickel

◀ **511441BB**
Burnished Bronze

24.50"W x 84.50"H

84.50"H Overall

Includes 6", 12" &

18"L Removable Rods

Canopy: 5"W x .75"H

4 – 60 Watt E12

Candelabra

Clear Glass Panels

Finishes: BB, PN

1' Chain; 6' Wire





◀ **9653WG**
Winter Gold
 26.75"W x 50"H
 Canopy: 5.25"W x 1.50"H
 8 – 60 Watt
 E12 Candelabra
 Finish: WG
 10' Chain; 15' Wire



▶ **9652WG**
Winter Gold
 20.25"W x 38.50"H
 Canopy: 5.25"W x 1.50"H
 6 – 60 Watt E12 Candelabra
 Finish: WG
 10' Chain; 15' Wire




◀ **9651WG**
Winter Gold
 13.25"W x 17.50"H
 Canopy: 5.25"W x 1.50"H
 3 – 60 Watt E12 Candelabra
 Finish: WG
 10' Chain; 15' Wire

9651WG FOYER
 Includes Flush
 Mount Option
 13.25" x 16.75"



◀ **9310BB**
Burnished Bronze
 17"W x 31.50"H
 Canopy: 5"W x 1"H
 3 – 60 Watt E12 Candelabra
 Clear Seeded Glass
 Finishes: BB, MN
 10' Chain; 15' Wire



▶ **9310MN**
Matte Nickel
 17"W x 31.50"H
 Canopy: 5"W x 1"H
 3 – 60 Watt E12 Candelabra
 Clear Seeded Glass
 Finishes: BB, MN
 10' Chain; 15' Wire



◀ **510241OB**
Old Bronze
 12"W x 17.50"H
 Canopy: 5"W x 1"H
 4 – 60 Watt E12 Candelabra
 Finish: OB
 10' Chain; 15' Wire

▶ **510242OB**
Old Bronze
 20"W x 30"H
 Canopy: 5"W x 1"H
 4 – 60 Watt
 E12 Candelabra
 Finish: OB
 10' Chain; 15' Wire





◀ **9101BB**
Burnished Bronze
 10.50"W x 12.75"H
 Canopy: 5"W x 1"H
 1 – 100 Watt E26 Medium
 Finish: BB
 6' Chain; 10' Wire



◀ **9102BB**
Burnished Bronze
 20"W x 22.75"H
 Canopy: 5"W x 1"H
 4 – 100 Watt E26 Medium
 Finish: BB
 6' Chain; 10' Wire

▶ **4523SY**
Surrey
 24"W x 41.25"H
 Canopy: 5"W x 1"H
 8 – 60 Watt E12
 Candelabra
 Finish: SY
 10' Chain;
 15' Wire



▶ **4522SY**
Surrey
 18"W x 30.50"H
 Canopy: 5"W x 1"H
 8 – 60 Watt E12
 Candelabra
 Finish: SY
 10' Chain;
 15' Wire



▶ **4521FO**
French Oak
 ▶ **4521SY**
Surrey
 12"W x 20.75"H
 Canopy: 5"W x 1"H
 4 – 60 Watt E12 Candelabra
 Finishes: FO, SY
 10' Chain; 15' Wire





◀ **510541GW**
Glossy White
 12"W x 18"H
 Canopy: 5"W x 1"H
 4 – 60 Watt E12
 Candelabra
 Finishes: GW, WG
 10' Chain; 15' Wire



◀ **510542GW**
Glossy White
 15"W x 26.50"H
 Canopy: 5"W x 1"H
 4 – 60 Watt E12
 Candelabra
 Finishes: GW, WG
 10' Chain; 15' Wire


▶ **510541WG**
Winter Gold
 12"W x 18"H
 Canopy: 5"W x 1"H
 4 – 60 Watt E12
 Candelabra
 Finishes: GW, WG
 10' Chain; 15' Wire



▶ **510542WG**
Winter Gold
 15"W x 26.50"H
 Canopy: 5"W x 1"H
 4 – 60 Watt E12
 Candelabra
 Finishes: GW, WG
 10' Chain; 15' Wire



▲ **512941BB**
Burnished Bronze
 12"W x 20.50"H
 Canopy: 5"W x .75"H
 4 – 60 Watt E12
 Candelabra
 Finishes: BB, SF
 10' Chain; 15' Wire



▼ **512942BB**
Burnished Bronze
 16.75"W x 25"H
 Canopy: 5"W x .75"H
 4 – 60 Watt E12
 Candelabra
 Finishes: BB, SF
 10' Chain; 15' Wire



▲ **512931BB**
Burnished Bronze
 16.50"W x 25"H x 14.25"E
 Canopy: 5"W x .75"H
 3 – 60 Watt E12
 Candelabra
 Finishes: BB, SF
 10' Chain; 15' Wire

► **512941SF**

Soft Gold
 12"W x 20.50"H
 Canopy: 5"W x .75"H
 4 – 60 Watt E12
 Candelabra
 Finishes: BB, SF
 10' Chain; 15' Wire



◀ **512942SF**

Soft Gold
 16.75"W x 25"H
 Canopy: 5"W x .75"H
 4 – 60 Watt E12
 Candelabra
 Finishes: BB, SF
 10' Chain; 15' Wire



▲ **510491SF**

Soft Gold
 25"W x 39.5"H
 Canopy: 5"W x .75"E
 9 – 60 Watt Candelabra
 Finish: SF
 10' Chain; 15' Wire



► **512931SF**

Soft Gold
 16.50"W x 25"H x 14.25"E
 Canopy: 5"W x .75"H
 3 – 60 Watt E12
 Candelabra
 Finishes: BB, SF
 10' Chain; 15' Wire



► **510441SF**

Soft Gold
 16"W x 26.75"H
 Canopy: 5"W x .75"E
 4 – 60 Watt Candelabra
 Finish: SF
 10' Chain; 15' Wire





◀ **9183RT** *Rustic*
31.25"W x 48.5"H
Canopy: 6"W x 1.5"H
8 – 60 Watt Candelevra
Finish: RT
10' Chain; 15' Wire



◀ **9182RT**
Rustic
22.5"W x 35.5"H
Canopy: 5.25"W x 1.25"H
6 – 60 Watt Candelevra
Finish: RT
10' Chain; 15' Wire



9181RT
Includes Flush
Mount Option
11"W x 18.5"H



◀ **9181RT**
Rustic
11"W x 19"H
Canopy: 5.25"W x 1.5"H
3 – 60 Watt Candelevra
Finish: RT
10' Chain; 15' Wire



◀ **4503SY**
Surrey
 24"W x 42.5"H
 Canopy: 5"W x 1"E
 8 – 60 Watt E12 Candelabra
 Finish: SY
 10' Chain; 15' Wire



▶ **4509SY**
Surrey
 20"W x 22.5"H
 Canopy: 5"W x 1"E
 6 – 60 Watt E12 Candelabra
 Finish: SY
 10' Chain; 15' Wire

▶ **4500SY**
Surrey
 9"W x 15"H
 Canopy: 5"W x 1"E
 4 – 60 Watt E12 Candelabra
 Finish: SY
 10' Chain; 15' Wire



4500SY
 Includes Semi-Flush Option
 9"W x 13.75"H



◀ **4501SY**
Surrey
 12"W x 21.75"H
 Canopy: 5"W x 1"E
 4 – 60 Watt E12 Candelabra
 Finish: SY
 10' Chain; 15' Wire



◀ **4502SY**
Surrey
 16"W x 29"H
 Canopy: 5"W x 1"E
 6 – 60 Watt E12 Candelabra
 Finish: SY
 10' Chain; 15' Wire



ALISA
▲ 4487PN-621
38"W x 53.50"H x 18"E
see page 29



AVANTI
▶ 817681RT-376
46"W x 35"H x 23.50"E
see page 45



BELMONT
◀ 3417BB

▶ 3417BB-149
36"W x 24"H x 13.25"E
see page 66



CHANDLER
▶ 3077BB
37"W x 23.50"H x 13"E
see page 112




CORRIGAN
▲ 810981AS-650
32"W x 68.25"H x 23"E
see page 141



island
collection




LOFT
 ▼ 3926MN-630
 38"W x 46"H x 16"E
 see page 205



MID-CENTURY
 ▲ 821151AD-426
 47"W x 58.75"H x 10"E
 see page 221

MID-CENTURY
 ▼ 821151PN-426
 47"W x 58.75"H x 10"E
 see page 221

LOFT
 ▼ 3926BB-629
 38"W x 46"H x 16"E
 see page 205



MORGAN
 ▲ 7004PN
 40"W x 71"H
 x 12"E
 see page 244



MORGAN
 ▲ 7004BB
 40"W x 71"H x 12"E
 see page 244




TAYLOR
 ▲ 4597PN-624
 37.25"W x 54.50"H x 18.25"E
 see page 320




TAYLOR
 ▲ 4597BB-622
 37.25"W x 54.50"H x 18.25"
 see page 320



WEST PORT
 ▲ 820181OB
 44"W x 71"H x 13"E
 see page 325



ZANDER
 ▲ 821901AD
 46"W x 57.50"H x 11.50"E
 see page 345



◀ 4656BB-603
Burnished Bronze
 ▼ 4656PN-603
Polished Nickel
 36.25"W x 25"H x 20"E
 Canopy: 11.50"L x 5.50"W x .75"E
 6 – 60 Watt E12 Candelabra
 Fabric Shade
 Finishes: BB, PN
 10' Chain; 15' Wire



◀ 812231BB
Burnished Bronze
 ▶ 812231BN
Brushed Nickel
 44"W x 31"H x 13"E
 Canopy: 5"W x 1"H
 3 – 60 Watt E26 Medium
 Frosted Glass Diffuser
 Finishes: BB, BN
 10' Chain; 15' Wire



pendant | collection



ALEXANDER
 ▲ 4744BB-611
 ► 4744WG-611
 24.25"W x 46"H
 see page 21



ARDEN
 ▲ 311241BS-317
 14.50"W x 52"H
 see page 36



ASHER
 ▲ 314941CZ-662
 18.50"W x 16.75"H
 see page 38



AXIS
 ◀ 4233WG-CR
 12.50"W x 13.25"H
 see page 49



AXIS
 ► 4233WG
 12.50"W x 13.25"H
 see page 49



AXIS
 ◀ 4233RS-CR
 12.50"W x 13.25"H
 see page 51



AXIS
 ► 4233RS PENDANT
 12.50"W x 13.25"H
 see page 51



AXIS
 ◀ 4233BN
 12.50"W x 13.25"H
 see page 51



AXIS
 ► 4233AB
 12.50"W x 13.25"H
 see page 47



AXIS
 ◀ 4234BN
 23"W x 23.50"H
 see page 51



AXIS
 ► 4234AB
 23"W x 23.50"H
 see page 47



pendant
collection

pendant | collection



AXIS
◀ 4234RS-CR
23"W x 23.50"H
see page 50



AXIS
◀ 4234WG-CR
23"W x 23.50"H
see page 48



AXIS
▶ 4234RS
23"W x 23.50"H
see page 50




AXIS
▶ 4234WG
23"W x 23.50"H
see page 48



AXIS
◀ 4236BN
30"W x 30.50"H
see page 51



AXIS
◀ 4236WG
30"W x 30.50"H
see page 48



AXIS
◀ 4236RS
30"W x 30.50"H
see page 50



AXIS
▶ 4236AB
30"W x 30.50"H
see page 47



AXIS
▶ 4236WG-CR
30"W x 30.50"H
see page 49



AXIS
▶ 4236RS-CR
30"W x 30.50"H
see page 50



BAILEY
 ▲ 4723WG
 15.25"W x 18.50"H
 see page 53



BAILEY
 ▲ 4720WG-565
 32"W x 34.25"H
 see page 53



BARCLAY
 ▲ 3581CB-287
 6.25"W x 45"H
 see page 56

BARCLAY
 ► 3584CB
 20.75"W x 28.5"H
 see page 56



BAXTER
 ◀ 4552BN-364
 ► 4552PN-364
 10"W x 61"H
 see page 61



BAXTER
 ◀ 4552BB-364
 ► 4552CH-364
 10"W x 61"H
 see page 61



BAXTER
 ▲ 4551BN-128
 ► 4551PN-128
 6.50"W x 7"H
 see page 60



BAXTER
 ▲ 4551BB-128
 ► 4551CH-128
 6.50"W x 7"H
 see page 60



pendant | collection



BELMONT
◀ 3414BB-SW
18.25"W x 26"H
see page 64



BELMONT
▶ 3414BB
18.25"W x 26"H
see page 64



BENNETT
◀ 511141RS-665
15"W x 24.25"H
see page 68



BENNETT
▲ 311131RS-664
14.75"W x 61"H
see page 68

BLAKELY
▶ 9484AG-CR
15"W x 16.50"H
see page 79



BLAKELY
◀ 9484AS-CR
▼ 9484CG-CR
15"W X 16.50"H
see page 79



BERKELEY
▲ 4964WG-617
21.50"W x 55.50"H
see page 71

4964WG-617
Includes Flush
Mount Option
21.50"W x 19.50"H





CAMBRIDGE
 ◀ 313641WG
 16"W x 21.50"H
 see page 93



CAMILLE
 ◀ 310741SF
 18.75"W x 21"H
 see page 99



CAMILLE
 ▶ 310731SF
 13.50"W x 16.25"H
 see page 99




CARRINGTON
 ◀ 3184WG-CR
 24.75"W x 62"H
 see page 105



CHAPMAN
 ◀ 3941BB-202
 ◀ 3941MN-202
 ▼ 3941BB-201
 5.75"W x 43"H
 see page 116



CHANDLER
 ◀ 3070MN-222
 8"W x 44"H
 see page 112



CHANDLER
 ◀ 3070BB-292
 8"W x 44"H
 see page 112

pendant | collection



CHAPMAN
 ◀ 3948BB-SW
 ▶ 3948BB-TW
 17.50"W x 22"H
 see page 117



CHAPMAN
 ◀ 3948MN-SW
 17.50"W x 22"H
 see page 117



CHARLESTON
 ◀ 313342SG
 15"W x 26.50"H
 see page 121

CITY
 ▶ 319201PN
 29"W x 63"H
 see page 131



CORRIGAN
 ▶ 210941AS-652
 15"W x 16.5"H
 see page 140



CHARLESTON
 ▶ 313341SG
 23"W x 29.50"H
 see page 121



CORRIGAN
 ▲ 310961AS-651
 24"W x 22.50"H
 see page 141

**210941AS-652
 CEILING**
 Includes Flush
 Mount Option
 15"W x 15"H





EASTMAN
 ▲ 4886SZ
 24.75"W x 14.25"H
 see page 151



EASTMAN
 ▲ 4883SZ
 15"W x 13.75"H
 see page 151



EASTMAN
 ▲ 4884SZ
 18"W x 14.50"H
 see page 151



ELLIS
 ◀ 4544AS-579
 ▼ 4544BG-579
 ▼ 4544CG-579
 10"W x 13.50"H
 see page 157



ELLIS
 ▲ 4545AS-582
 ▲ 4545BG-582
 ▶ 4545CG-582
 18.25"W x 14"H
 see page 155



4545AS-582
 4545BG-582
 4545CG-582
 Includes
 Semi-Flush
 Mount Option
 18.25"W x 15.50"H



ELLIS
 ◀ 4543AS-578
 ▶ 4543BG-578
 ▶ 4543CG-578
 22"W x 21"H
 see page 156



pendant | collection



ELLIS
 ◀ 4541AS
 18"W x 20.25"H
 see page 154




ELLIS
 ◀ 4541BG
 18"W x 20.25"H
 see page 154




ELLIS
 ◀ 4541CG
 18"W x 20.25"H
 see page 154



ELLIS
 ◀ 4542AS
 26"W x 28.25"H
 see page 153



ELLIS
 ◀ 4542BG
 26"W x 28.25"H
 see page 153



ELLIS
 ▶ 4542CG
 26"W x 28.25"H
 see page 153

**9172WG
 PENDANT**
 Includes Flush
 Mount Option
 10"W x 20"H



FIFTH AVENUE
 ◀ 9172WG
 10"W x 20"H
 see page 166

FIFTH AVENUE
 ▶ 4005WG-486
 22"W x 53.50"H
 see page 166



FIFTH AVENUE
 ▶ 4001WG-485
 7"W x 53.50"H
 see page 164





HARLOW
▶ 4494SQ-569-CR
17"W x 21.25"H
see page 178

FIRE AND ICE
◀ 320841FI
12"W x 16"H
see page 170



HILL HOUSE
◀ 3564BB
21"W x 30"H
see page 182



HILL HOUSE
▲ 3561BB-252
6"W x 46"H
see page 180

JACKSON
▶ 4890OR
8"W x 64.25"H
see page 191



JACKSON
◀ 4898OR
15"W x 20.50"H
see page 191



JACKSON
◀ 4896OR
32"W x 23.50"H
see page 189



JACKSON
◀ 4894OR
21.75"W x 12.50"H
see page 189



JULIETTE
◀ 312141WG
15"W x 23"H
see page 193



JULIETTE
◀ 312161WG
22.50"W x 29"H
see page 193

JULIETTE
▶ 312162WG
26"W x 30.25"H
see page 193



pendant | collection

LOFT

▶ 3922BB-613
 ▼ 3922MN-623
 24"W x 50.50"H
 see page 207



LOWELL

◀ 4796TZ
 24"W x 30"H
 see page 209



LOWELL

▶ 4794TZ
 18.25"W x 23.75"H
 see page 209



LOWELL

◀ 4793TZ
 13.50"W x 19"H
 see page 209



MARGO

▶ 4224WG-551-CR
 20"W x 18.25"H
 see page 215



4224WG-551-CR

Includes
 Semi-Flush
 Mount Option
 20"W x 18"H



MERCER

◀ 321242WG
 25.25"W x 25.50"H
 see page 218



MERCER

◀ 321243WG-CR
 26.25"W x 31"H
 see page 218



MERCER

▲ 321241WG
 18"W x 19.50"H
 see page 218





MID-CENTURY
▲ 321151AD-426
21.50"W x 64.25"H
see page 222



MID-CENTURY
▲ 321151PN-426
21.50"W x 64.25"H
see page 222



MID-CENTURY
▲ 321142AD
15.50"W x 65"H
see page 224



MID-CENTURY
▲ 321142PN
15.50"W x 65"H
see page 224



321111AD
321111PN
PENDANT
Includes
Semi-Flush Option
11.25"W x 15"H



MID-CENTURY
▶ 321111AD
▶ 321111PN
11.25"W x 50.75"H
see page 222



MIDTOWN
▲ 318821BB-669
▲ 318821PN-669
8.75"W x 65"H
see page 228



MIDTOWN
◀ 318821MN-669
◀ 318821BB-670
8.75"W x 65"H
see page 228

pendant | collection



MIDTOWN
 ◀ 3911MN-400
 ▼ 3911BB-400
 24"W x 49.50"H
 see page 229



MIDTOWN
 ◀ 3911PN-400
 ▼ 3911BB-401
 24"W x 49.50"H
 see page 229



MIDTOWN
 ◀ 3910MN-457
 ▼ 3910BB-457
 18"W x 49"H
 see page 230



MIDTOWN
 ◀ 3910PN-457
 ▼ 3910BB-456
 18"W x 49"H
 see page 230



MILAN
 ◀ 319741CG-675
 15"W x 13"H
 see page 240



MILAN
 ▶ 319742CG-676
 24"W x 17.25"H
 see page 241



O'NEAL
 ◀ 3797BB
 9.50"W x 9"H
 see page 252



O'NEAL
 ▲ 3798BB
 15"W x 10"H
 see page 252



PERRY
◀ 4864BA
13"W x 18"H
see page 263



PERRY
◀ 4866BA
23"W x 28.50"H
see page 263

PERRY
▶ 4864PN
13"W x 18"H
see page 263



PERRY
▶ 4866PN
23"W x 28.50"H
see page 263



REGAN
◀ 319441CG-437-LD
6.50"W x 64.25"H
see page 276



REID
▲ 312042RT
18"W x 15.75"H
see page 278



RENAISSANCE
▼ 321541RN
18"W x 19.75"H
see page 285

pendant | collection



RIVER CREST
◀ 3601RI-125
4.50"W x 20"H
see page 286



RIVIERA
◀ 310611AS-301
12"W x 59"H
see page 291



RIVIERA
▶ 310631AS-301
24"W x 18"H
see page 291



STANTON
◀ 4031BB-207
◀ 4031BB-212
◀ 4031BN-212
6.75"W x 43"H
see page 306




STANTON
◀ 4038BB-SW
◀ 4038BN
◀ 4038BB
20.50"W x 23"H
see page 307



STEELE
 ◀ 4340BN-103
 ◀ 4340BB-103
 6.25"W x 43.50"H
 see page 311



STUDIO
 ◀ 3870PN-492
 8"W x 52.50"H
 see page 317



STUDIO
 ◀ 3875PN-495
 24"W x 57"H
 see page 317



TAYLOR
 ◀ 4593BB-607
 12"W x 17.75"H
 see page 321



TAYLOR
 ◀ 4593PN-594
 12"W x 17.75"H
 see page 321



TAYLOR
 ▶ 4594BB-605
 24"W x 24.25"H
 see page 321



TAYLOR
 ▶ 4594PN-592
 24"W x 24.25"H
 see page 321



pendant | collection

▶ **322041SL**

Silver Leaf

▶ **322041CG**

Capital Gold

16"W x 19"H
 Canopy: 5"W x 1"H
 4 – 60 Watt E12
 Candelabra
 Finishes: CG, SL
 10' Chain;
 15' Wire



▶ **322042SL**

Silver Leaf

▶ **322042CG**

Capital Gold

22.75"W x 26"H
 Canopy: 5"W x 1"H
 6 – 60 Watt E12
 Candelabra
 Finishes:
 CG, SL
 10' Chain;
 15' Wire



◀ **322611BB**

Burnished Bronze

◀ **322611BN**

Brushed Nickel

◀ **322611PN**

Polished Nickel

11.50"W x 20"H
 Canopy: 5"W x .75"H
 1 – 100 Watt E26 Medium
 Finishes: BB, BN, PN
 10' Chain; 15' Wire

▶ **322641BB**

Burnished Bronze

▶ **322641BN**

Brushed Nickel

▶ **322641PN**

Polished Nickel

16.50"W x 28"H
 Canopy: 5"W x .75"H
 4 – 60 Watt
 E12 Candelabra
 Finishes: BB, BN, PN
 10' Chain; 15' Wire



▶ **4906IA**

Iron and Oak

25.75"W x 26.50"H

Canopy: 5"W x 1"H

6 – 60 Watt E12 Candelabra

Finishes: IA, PN

10' Chain; 15' Wire



▶ **4906PN**

Polished Nickel

25.75"W x 26.50"H

Canopy: 5"W x 1"H

6 – 60 Watt E12 Candelabra

Finishes: IA, PN

10' Chain; 15' Wire



◀ **311841SF**

Soft Gold

16"W x 21.75"H

Canopy: 5"W x 1"H

4 – 60 Watt

E12 Candelabra

Finish: SF

10' Chain;

15' Wire



◀ **311861SF**

Soft Gold

23"W x 28.50"H

Canopy: 5"W x 1"H

6 – 60 Watt

E12 Candelabra

Finish: SF

10' Chain;

15' Wire



◀ **312542BI**

Black Iron

23"W x 74"H

74"H Overall Includes 6",

12" & 18"L Removable Rods

Canopy: 5"W x 1"H

4 – 60 Watt

E12 Candelabra

Finish: BI

1' Chain; 6' Wire



◀ **312541BI**

Black Iron

18.50"W x 70"H

70"H Overall Includes 6",

12" & 18"L Removable Rods

Canopy: 5"W x 1"H

4 – 60 Watt

E12 Candelabra

Finish: BI

1' Chain; 6' Wire

pendant | collection

▼ **4835BN-616**

Brushed Nickel
 28"W x 49"H
 49"H Overall
 Includes 6", 12" & 18"L
 Removable Rods
 Canopy: 5"W x 1"H
 4 – 60 Watt E26 Medium
 Decorative White
 Fabric Shade
 Finish: BN
 1' Chain; 6' Wire



▶ **4831BN-614**

Brushed Nickel
 10"W x 49"H
 49"H Overall
 Includes 6", 12" & 18"L
 Removable Rods
 Canopy: 5"W x 1"H
 2 – 60 Watt E12
 Candelabra
 Decorative White
 Fabric Shade
 Finish: BN
 1' Chain; 6' Wire



▼ **4833BN-612**

Brushed Nickel
 18"W x 45.50"H
 45.50"H Overall
 Includes 6", 12" & 18"L
 Removable Rods
 Canopy: 5"W x 1"H
 3 – 60 Watt
 E26 Medium
 Decorative White
 Fabric Shade
 Finish: BN
 1' Chain; 6' Wire



◀ **4548DB-581**

Dark Bronze
 18"W x 11.50"H
 Canopy: 5"W x .75"H
 1 – 100 Watt
 E26 Medium
 Decorative Tan
 Fabric Shade
 Finish: DB
 8' Wire



◀ **4548DB-577**

Dark Bronze
 18"W x 11.50"H
 Canopy: 5"W x .75"H
 1 – 100 Watt
 E26 Medium
 Decorative Light Tan
 Fabric Shade
 Finish: DB
 8' Wire



◀ **4216BG-544-CP**

Brushed Gold
 24"W x 15.50"H
 Canopy: 5"W x 0.75"H
 6 – 60 Watt E12 Candelabra
 Decorative White
 Fabric Shade
 Finish: BG
 6' Chain; 10' Wire



4216BG-544-CP

Includes
 Semi-Flush
 Mount Option
 24"W x 14"H



▶ **2720BB**

Burnished Bronze
 20"W x 20.75"H
 Canopy: 5"W x 1"H
 3 – 100 Watt E26 Medium
 Mist Scavo Glass
 Finish: BB
 6' Wire; 10' Wire
 Adjustable to 13.5"H



**2720BB
 2720MN
 PENDANT**

Includes
 Flush Mount Option
 20"W x 21.25"H



◀ **2720MN**

Matte Nickel
 20"W x 20.75"H
 Canopy: 5"W x 1"H
 3 – 100 Watt E26 Medium
 White Faux
 Alabaster Glass
 Finish: MN
 6' Wire; 10' Wire
 Adjustable to 13.5"H



▶ **312221BB**

Burnished Bronze

▶ **312221BN**

Brushed Nickel

17.75"W x 64.50"H
 64.50"H Overall Includes
 6", 12" & 18"L
 Removable Rods
 Canopy: 5.75"W x 1.50"H
 2 – 60 Watt E26 Medium
 Frosted Glass Diffuser
 Finishes: BB, BN
 1' Chain; 6' Wire



▶ **312211BB**

Burnished Bronze

▶ **312211BN**

Brushed Nickel

13"W x 62"H . 62"H
 Overall Includes 6", 12"
 & 18"L Removable Rods
 Canopy: 5.75"W x 1.50"H
 1 – 60 Watt E26 Medium
 Frosted Glass Diffuser
 Finishes: BB, BN
 1' Chain; 6' Wire



◀ **312811BN**

Brushed Nickel

◀ **312811WZ**

Weathered Zinc

◀ **312811GM**

Gunmetal

◀ **312811BB**

Burnished Bronze

18"W x 61.25"H
 61.25"H Overall Includes 6",
 12" & 18"L Removable Rods
 Canopy: 5"W x 1"H
 1 – 100 Watt E26 Medium
 Finishes: BB, BN, GM, WZ
 1' Chain; 6' Wire



pendant | collection

◀ **4190BB**

Burnished Bronze
10"W x 41"H
41"H Overall Includes
6", 12" & 18"L
Removable Rods
Canopy: 6.25"W x 1"H
1 – 75 Watt E26 Medium
Finishes: BB, GR
1' Chain; 6' Wire



◀ **4568BB**

Burnished Bronze
16.50"W x 46"H
46"H Overall Includes 6",
12" & 18"L Removable Rods
Canopy: 5"W x 1.25"H
1 – 100 Watt E26 Medium
Metal Shade
Finish: BB
1' Chain; 6' Wire
Damp Rated



▶ **4190GR**

Graphite
10"W x 41"H
41"H Overall Includes
6", 12" & 18"L
Removable Rods
Canopy: 6.25"W x 1"H
1 – 75 Watt E26 Medium
Finishes: BB, GR
1' Chain; 6' Wire



▶ **4567BB**

Burnished Bronze
10.50"W x 45.25"H
45.25"H Overall Includes 6",
12" & 18"L Removable Rods
Canopy: 5"W x 1.25"H
1 – 100 Watt E26 Medium
Finish: BB
1' Chain; 6' Wire
Damp Rated



▶ **9638OB**

Old Bronze

▶ **9638GR**

Graphite

6.75"W x 11.75"H
Canopy: 6.25"W x 1"H
1 – 100 Watt E26 Medium
Clear Seeded Glass
Finishes: GR, OB
8' Wire





- ◀ **4432BB**
Burnished Bronze
- ◀ **4432PN**
Polished Nickel
- ◀ **4432AN**
Antique Nickel

13"W x 51"H
51"H Overall Includes 6", 12"
& 18"L Removable Rods
Canopy: 5.50"W x 1"H
1 – 100 Watt E26 Medium
Optional Frosted Glass Diffuser
Finishes: AN, BB, PN
1' Chain; 6' Wire



- ◀ **4433BB**
Burnished Bronze
- ◀ **4433PN**
Polished Nickel
- ◀ **4433AN**
Antique Nickel

19"W x 56.25"H
56.25"H Overall Includes 6",
12" & 18"L Removable Rods
Canopy: 5.50"W x 1"H
1 – 100 Watt E26 Medium
Optional Frosted Glass Diffuser
Finishes: AN, BB, PN
1' Chain; 6' Wire

- ▶ **4431BB**
Burnished Bronze
- ▶ **4431PN**
Polished Nickel
- ▶ **4431AN**
Antique Nickel

9"W x 48.50"H
48.50"H Overall Includes 6",
12" & 18"L Removable Rods
Canopy: 5.50"W x 1"H
1 – 100 Watt E26 Medium
Finishes: AN, BB, PN
1' Chain; 6' Wire



pendant | collection



◀ **3531BB-134**
Burnished Bronze
◀ **3531PN-134**
Polished Nickel

10.50"W x 46"H
46"H Overall Includes 6", 12"
& 18"L Removable Rods
Canopy: 5"W x 1.25"H
1 – 75 Watt E26 Medium
Clear Glass
Finishes: BB, PN
1' Chain; 6' Wire



◀ **3531BB-129**
Burnished Bronze
◀ **3531PN-129**
Polished Nickel

10.50"W x 46"H
46"H Overall Includes 6", 12"
& 18"L Removable Rods
Canopy: 5"W x 1.25"H
1 – 75 Watt E26 Medium
Milk Glass
Finishes: BB, PN
1' Chain; 6' Wire

▶ **4751BN-153**

Brushed Nickel
6.75"W x 50"H
50"H Overall Includes 6",
12" & 18"L Removable Rods
Canopy: 5"W x 1"H
1 – 60 Watt E12 Candelabra
Milk Glass
Finish: BN
1' Chain; 6' Wire



▶ **4752BN-154**

Brushed Nickel
6.75"W x 58"H
58"H Overall Includes 6",
12" & 18"L Removable Rods
Canopy: 5"W x 1"H
2 – 60 Watt E12 Candelabra
Milk Glass
Finish: BN
1' Chain; 6' Wire



▶ **317312BB-LD**

Burnished Bronze

▶ **317312BN-LD**

Brushed Nickel

▶ **317312PN-LD**

Polished Nickel

15.75"W x 59"H

59"H Overall Includes

6", 12" & 18"L

Removable Rods

Canopy: 5"W x 1"H

Lumens: 2250, CR > 80,

Volts/Wattage:

120 Volts 50/60 HZ/25W

Color Temperature: 3000K

Frosted Glass Diffuser

Finishes: BB, BN, PN

1' Chain; 6' Wire

[LED]



**Dimmable – LED
Dimmer Recommended**



▶ **317311BB-LD**

Burnished Bronze

▶ **317311PN-LD**

Polished Nickel

▶ **317311BN-LD**

Brushed Nickel

11.75" W x 59.50" H.

59.5" Overall

Includes 6", 12" & 18"L

Removable Rods

Canopy: 5"W x 1"H

Lumens: 1350, CR > 80,

Volts/Wattage:

120 Volts 50/60 HZ/15W

Color Temperature: 3000K

Frosted Glass Diffuser

Finishes: BB, BN, PN

1' Chain; 6' Wire

[LED]

**Dimmable – LED
Dimmer Recommended**



▲ **311511BB-321**

Burnished Bronze · Milk Glass

▲ **311511PN-320**

Polished Nickel · Clear Glass

19"W x 60.75"H

60.75"H Overall Includes

6", 12" & 18"L Removable Rods

Canopy: 5"W x 1"H

1 – 100 Watt E26 Medium

1' Chain; 6' Wire

pendant | collection



◀ **4643BB-138**
Burnished Bronze
 ▼ **4643PN-138**
Polished Nickel
 7.50"W x 10.75"H
 Canopy: 5"W x 1"H
 1 – 100 Watt
 E26 Medium
 Clear Glass
 Finishes: BB, PN
 8' Wire



◀ **4644BB-143**
Burnished Bronze
 ▼ **4644PN-143**
Polished Nickel
 8.25"W x 11.25"H
 Canopy: 5"W x .75"H
 1 – 100 Watt
 E26 Medium
 Clear Glass
 Finishes: BB, PN
 8' Wire



◀ **4642AD-137**
Aged Brass
 ◀ **4642BB-137**
Burnished Bronze
 ◀ **4642PN-137**
Polished Nickel
 8.50"W x 10.50"H
 Canopy: 5"W x 1"H
 1 – 100 Watt E26 Medium
 Clear Glass
 Finishes: AD, BB, PN
 8' Wire



◀ **4641BB-136**
Burnished Bronze
 ◀ **4641GA-136**
Graphite With Aged Brass
 ◀ **4641PN-136**
Polished Nickel
 10.25"W x 12.75"H
 Canopy: 5"W x 1"H
 1 – 100 Watt E26 Medium
 Clear Glass
 Finishes: BB, GA, PN
 8' Wire

► **319911BN**

Brushed Nickel

► **319911PN**

Polished Nickel

► **319911BB**

Burnished Bronze

15.50"W x 60.50"H

60.50"H Overall Includes

6", 12" & 18"L Removable Rods

Canopy: 5"W x 1"H

1 – 100 Watt E26 Medium

Clear Glass

Finishes: BB, BN, PN

1' Chain; 6' Wire



► **319913BN**

Brushed Nickel

► **319913PN**

Polished Nickel

► **319913BB**

Burnished Bronze

15.75"W x 60.50"H

60.50"H Overall Includes

6", 12" & 18"L Removable Rods

Canopy: 5"W x 1"H

1 – 100 Watt E26 Medium

Clear Glass

Finishes: BB, BN, PN

1' Chain; 6' Wire



► **319912BN**

Brushed Nickel

► **319912PN**

Polished Nickel

► **319912BB**

Burnished Bronze

10.50"W x 64"H

64"H Overall Includes

6", 12" & 18"L Removable Rods

Canopy: 5"W x 1"H

1 – 100 Watt E26 Medium

Clear Glass

Finishes: BB, BN, PN

1' Chain; 6' Wire



pendant | collection



◀ **3718BB-135**
Burnished Bronze
 ▶ **3718BN-135**
Brushed Nickel
 ▶ **3718GA-135**
Graphite With Aged Brass
 ▶ **3718PN-135**
Polished Nickel
 6"W x 9.25"H
 Canopy: 5"W x 1.25"H
 1 – 100 Watt E26 Medium
 Clear Glass
 Finishes: BB, BN, GA, PN
 8' Wire

▶ **3907BB**
Burnished Bronze
 ▶ **3907MN**
Matte Nickel
 15"W x 9"H
 Canopy: 5"W x 1"H
 1 – 150 Watt
 E26 Medium
 White Faux
 Alabaster Glass
 Finishes: BB, MN
 3' Chain; 10' Wire
 Damp Rated




▶ **317911OB**
Old Bronze
 9.75"W x 10.50"H
 Canopy:
 5"W x .75"H
 1 – 60 Watt
 E26 Medium
 Clear Seeded Glass
 Finish: OB
 8' Wire



◀ **3150MN-220**
Matte Nickel
 7.50"W x 45.25"H
 42.25"H Overall Includes 6",
 12" & 18"L Removable Rods
 Canopy: 5.25"W x 2.25"H
 1 – 100 Watt E26 Medium
 White Faux Alabaster Glass
 Finish: MN
 1' Chain; 6' Wire



◀ **3150MN-224**
Matte Nickel
 10"W x 45.75"H
 45.75"H Overall Includes 6",
 12" & 18"L Removable Rods
 Canopy: 5.25"W x 2.25"H
 1 – 100 Watt E26 Medium
 White Faux Alabaster Glass
 Finish: MN
 1' Chain; 6' Wire



◀ **3070BB-224**
Burnished Bronze
 10"W x 45.25"H
 45.25" Overall
 Including 6", 12" &
 18"L Removable Rods
 Canopy: 5.25"W x 2.25"H
 1 – 100 Watt Medium
 White Faux
 Alabaster Glass
 Finish: BB
 1' Chain; 6' Wire





▲ **PENDANTPN-32**
MULTI-PORT CANOPY
Polished Nickel
 31.75"L x 4.75"W x 1.25"H
 Finishes: BB, BN, PN

Round Multi-Port Canopies

- ▶ **721101BB**
Burnished Bronze
 - ▶ **721101AD**
Aged Brass
 - ▶ **721101PN**
Polished Nickel
 - ▶ **721101BN**
Brushed Nickel
- 18.50"W x 1.75"H
 Finishes: AD, BB, BN, PN



Rectangular Multi-Port Canopies



- ◀ **PENDANTBB-18**
Burnished Bronze
 - ◀ **PENDANTBN-18**
Brushed Nickel
 - ◀ **PENDANTPN-18**
Polished Nickel
- 18.25"L x 4.75"W
 Canopy: 1.25"H
 Finishes: BB, BN, PN

- ◀ **PENDANTBB-32**
Burnished Bronze
 - ◀ **PENDANTBN-32**
Brushed Nickel
- 31.75"L x 4.75"W
 Canopy: 1.25"H
 Finishes: BB, BN, PN

- ◀ **PENDANTBB-34**
Burnished Bronze
 - ◀ **PENDANTBN-34**
Brushed Nickel
 - ◀ **PENDANTPN-34**
Polished Nickel
- 34"L x 5"W
 Canopy: 1.25"H
 Finishes: BB, BN, PN



ADELE
▲ 4443SQ-000
18.50"W x 20"H
see page 16

ALISA
▶ 4488PN-574-CR
20.25"W x 14.75"H
see page 28



ALISA
◀ 4483PN-573-CR
17"W x 19.50"H
see page 28



ARDEN
▲ 311241BS-317
14.50"W x 15"H
see page 36

ASHER
▶ 314941CZ-662
18.50"W x 16.75"H
see page 38





petite
collection

ROBERT LONGO — CHARCOAL
MAPPLETHORPE Perfection in Form
Another ArtBook



BAILEY
▲ 4724WG-000
17.50"W x 18.50"H
see page 54



BLAKELY
◀ 4184AS-CR
18"W x 21.50"H
see page 79



BLAKELY
▶ 4184CG-CR
18"W x 21.50"H
see page 79



CAMBRIDGE
▲ 313641WG
16"W x 21.50"H
see page 93



BLAKELY
◀ 4184AG-CR
18"W x 21.50"H
see page 79



CHASTAIN
 ◀ 4204TB
 14"W x 13"H
 see page 125



CHATEAU
 ◀ 4094FO
 15.50"W x 23"H
 see page 129



4094FO
 Includes Flush
 Mount Option

EMERY
 ▶ 4734BN-150
 15.75"W x 17"H
 see page 158



FIFTH AVENUE
 ◀ 4007WG-500
 18"W x 22"H
 see page 165



GAVIN
 ▶ 421481IG
 16"W x 16.50"H
 see page 175



HARLOW
 ▶ 4494SQ-569-CR
 17"W x 21.25"H
 see page 178





HUTTON
◀ 4264WG-568
19.25"W x 21.50"H
see page 186



JULIETTE
▲ 312141WG
15"W x 23"H
see page 193

HUTTON
▶ 4263WG-552
20"W x 18.75"H
see page 186



MARGO
◀ 4224WG-551-CR
20"W x 18.25"H
see page 215

4224WG-551-CR
Includes Semi-Flush
Mount Option



MILAN
▲ 319741CG-675
15"W x 13"H
see page 240

MID-CENTURY
 ► 421141PN-426
 17.25"W x 16"H
 see page 223



MID-CENTURY
 ◀ 421141AD-426
 17.25"W x 16"H
 see page 223



RIVER CREST
 ◀ 3604RI-279
 19.50"W x 21"H
 see page 287



WYATT
 ◀ 4254SY-000
 20"W x 22.50"H
 see page 337



◀ 4802FW-CR
French White
 14.50"W x 20.50"H
 Canopy: 5"W x 1"H
 4 – 60 Watt E12
 Candelabra
 Finish: FW
 Clear Crystals
 10' Chain; 15' Wire



◀ 4801AS-CR
Antique Silver
 17.25"W x 22.75"H
 Canopy: 5"W x 1"H
 4 – 60 Watt E12
 Candelabra
 Finish: AS
 Clear Crystals
 10' Chain; 15' Wire



ABELLA
 ◀ 623011CG
 6"W x 20"H x 5"E
 see page 13



ADELE
 ▲ 4442SQ-000
 10.25"W x 18"H x 5"E
 see page 16

ALEXANDER
 ▶ 8061WG
 5.5"W x 14"H x 4"E
 see page 24
ADA



ALEXANDER
 ◀ 8061BB
 5.5"W x 14"H x 4"E
 see page 24
ADA

ALEXANDER
 ▶ 8062BB
 ▼ 8062WG
 11.50"W x 11.50"H x 4"E
 see page 24
ADA



ALEXANDER LED
 ▶ 8071BB-LD
 ▶ 8071WG-LD
 9"W x 7"H x 4"E
 see page 24
ADA



Dimmable – LED
 Dimmer Recommended



ALISA
 ◀ 8027PN-573-CR
 12.50"W x 15.50"H
 x 5.75"E
 see page 28

ALISA
 ▶ 8026PN-573-CR
 5"W x 15.50"H x 5.75"E
 see page 28



ALISA
 ◀ 8021PN-127
 5"W x 7.75"H x 6.25"E
 see page 29



sconce
collection



ALSTON
◀ **621014OB**
9.50"W x 9.50"H
x 5.50"E
see page 33



ALSTON
▶ **621013OB**
8"W x 12.75"H
x 5.50"E
see page 33



ALSTON
▶ **621012OB-654**
6"W x 21.50"H x 7"E
see page 33



ASHER
◀ **614911CZ-660**
6.75"W x 18"H x 7.75"E
see page 39

AVANTI
▶ **617611RT-376**
8"W x 15"H x 7.5"E
see page 44



ARDEN
▶ **611211BS-317**
6"W x 18"H x 8.75"E
see page 36



BAXTER
 ▲ 8301PN-128
 ► 8301BN-128

6.50"W x 10"H x 8.25"E
 see page 62



BAXTER
 ◀ 8301CH-128
 ▼ 8301BB-128

6.50"W x 10"H x 8.25"E
 see page 62



BELMONT
 ► 1331BB-242
 ▼ 1331BB-287

6"W x 8.50"H x 6.50"E
 see page 66



BENNETT
 ◀ 61111RS-653

6.75"W x 17.50"H
 x 8.25"E
 see page 68



BERKELEY
 ► 4961WG-000

4.50"W x 14.50"H
 x 4"E
 see page 70
ADA


BLAIR
 ► 8551AS-299

5.25"W x 9.50"H x 6.75"E
 see page 75



BLAIR
 ► 4941AS-635

10"W x 18.75"H x 5.25"E
 see page 74



BLAIR
 ▲ 4942AS-636

12.50"W x 10"H x 5.50"E
 see page 74



BLAKELY

- ◀ 1616AG-CR
- ◀ 1616AS-CR
- ◀ 1616CG-CR

5"W x 13.25"H
x 4.25"E
see page 78

BLAKELY

- ▼ 1617AG-CR
- ▼ 1617AS-CR
- ▼ 1617CG-CR

7"W x 12.50"H x 4.25"E
see page 81



BLAKELY

- ◀ 8521AS-CR
- 5"W x 7.75"H x 6"E
see page 84



BLAKELY

- ▶ 8521AG-CR
- 5"W x 7.75"H x 6"E
see page 84



BLAKELY

- ◀ 8521CG-CR
- 5"W x 7.75"H x 6"E
see page 84

BODEN

- ▶ 612311BN-324
- ▶ 612311BB-324

5"W x 15.25"H
x 8.50"E
see page 87



CAMBRIDGE

- ▶ 613611WG

5"W x 22.50"H
x 6.50"E
see page 92



CARLYLE

- ◀ 611711GS-654

6"W x 20.25"H
x 7.75"E
see page 102

CELINE

▶ **4781AS-000**
5.50"W x 19.25"H
x 9.50"E
see page 106



CHANDLER
◀ **1781MN-222**
◀ **1781BB-292**
8"W x 10.25"H
x 9.50"E
see page 112

CHARLESTON

▶ **613311SG-654**
6"W x 17.50"H x 11.50"E
see page 121



CHAPMAN
▲ **8401BB-202**
◀ **8401MN-202**
▶ **8401BB-201**
6"W x 9"H x 7.50"E
see page 114



CHASTAIN
◀ **1716TB-546**
5.25"W x 18.50"H x 6.25"E
see page 124



CHASTAIN
▶ **1717TB-546**
11.50"W x 12.50"H
x 6"E
see page 124



CHATEAU
◀ **1607FO**
7.75"W x 19"H x 5.50"E
see page 128

CHATEAU
▶ **1606FO**
5.25"W x 16.25"H
x 6.25"E
see page 128



CITY

▶ **619281PN**

11.50"W x 19"H x 4"E
see page 132



CORRIGAN

▶ **610911AS-315**

6.25"W x 16"H
x 6.75"E
see page 141



COLE

◀ **621311AO**

5.25"W x 18"H x 7"E
see page 137

COVINGTON

◀ **6301AN-489**

▶ **6301BB-489**

5"W x 15.50"H
x 5.25"E
see page 142



DAWSON

▶ **619311AD-674**

6"W x 17"H x 8"E
see page 148



EASTMAN

▶ **4881SZ**

5"W x 12"H
x 4"E

see page 151

ADA



ELLIS

▲ **4546AS-566**

▲ **4546CG-566**

◀ **4546BG-566**

10"W x 12"H x 5"E
see page 154



EMERY

▲ **8041BN-150**

4.50"W x 9"H x 4"E
see page 159

ADA



EVERLEIGH
 ▶ 61771FG-660
 6.75"W x 21"H
 x 9.50"E
 see page 162



FIFTH AVENUE
 ▼ 1986WG-484
 6"W x 15.50"H
 x 8"E
 see page 167

FIFTH AVENUE
 ▲ 1987WG-484
 14.50"W x 14"H x 8"E
 see page 167



FIRE AND ICE
 ◀ 620811FI
 6"W x 18.50"H
 x 4"E
 see page 170



FLYNN
 ◀ 611011GM-316
 5"W x 14.25"H
 x 6.75"E
 see page 173

GAVIN
 ▶ 621461IG
 7"W x 14.25"H
 x 3.75"E
 see page 176
ADA



HARLOW
 ▶ 4491SQ-570-CR
 8.50"W x 13.25"H x 9.75"E
 see page 178

HARLOW
 ▼ 4492SQ-571-CR
 26"W x 11.75"H x 9.25"E
 see page 178



HILL HOUSE
 ◀ 1886BB-252
 6"W x 12.50"H x 7"E
 see page 181



HUDSON
 ◀ 611911PN
 6"W x 20.50"H x 5.25"E
 see page 185

HUTTON
 ▶ 4261WG-552
 6.75"W x 12.50"H x 8.75"E
 see page 186






JACKSON
 ◀ 4897OR
 7.25"W x 17.75"H
 x 5"E
 see page 190

JACKSON
 ▼ 4892OR
 12"W x 10.50"H x 5.25"E
 see page 190



JACKSON
 ▶ 4891OR
 5"W x 13.25"H
 x 6.75"E
 see page 191



JACKSON
 ▲ 4899OR
 7.25"W x 8"H x 5"E
 see page 190



KINGSLEY
 ◀ 618721DS-668
 10.50"W x 17"H x 4.25"E
 see page 194



KNOX
 ▶ 62031OB-421
 8.25"W x 14.75"H
 x 10.25"E
 see page 198



LEIGH
 ◀ 4701BB-000
 5.75"W x 14"H
 x 5.25"E
 see page 201

LOFT
 ▶ 1981BB-468
 6"W x 14.50"H x 7"E
 see page 207



LOFT
 ▲ 1981BB-469
 6"W x 14.50"H x 7"E
 see page 207



LOFT
 ▲ 1981MN-469
 6"W x 14.50"H x 7"E
 see page 207



LUNA
 ▼ 1017WG-526
 11.50"W x 10"H x 4"E
 see page 211
ADA



LUNA
 ▲ 1027WG-410
 17"W x 7.75"H x 8.75"E
 see page 210



LUNA
 ▲ 1026WG-410
 7"W x 12.75"H x 8.50"E
 see page 210



MANHATTAN
 ◀ 62061PN-423
 5.25"W x 17.50"H x 7"E
 see page 213



MARGO
 ▲ 4221WG-549-CR
 6.75"W x 10.50"H x 8"E
 see page 215

MAXWELL
 ► 4531CB-000
 9"W x 15.75"H
 x 5.50"E
 see page 216



MERCER
 ◀ 621211WG-CR-671
 5"W x 20.50"H x 7"E
 see page 219

MERCER
 ► 621212WG-654
 6"W x 22.50"H x 7"E
 see page 219



MIDTOWN
 ▼ 1231BB-451
 6"W x 15.75"H x 7"E
 see page 234



MIDTOWN
 ▲ 1232BB-451
 15"W x 17"H x 7"E
 see page 234



MIDTOWN
 ▲ 1232BB-450
 15"W x 17"H x 7"E
 see page 235

MIDTOWN
 ▼ 1231BB-450
 6"W x 15.75"H x 7"E
 see page 235



MIDTOWN
▼ 1231MN-451
6"W x 15.75"H x 7"E
see page 236



MIDTOWN
▲ 1232MN-451
15"W x 17"H x 7"E
see page 236



MIDTOWN
▲ 1232PN-451
15"W x 17"H x 7"E
see page 237

MIDTOWN
▼ 1231PN-451
6"W x 15.75"H x 7"E
see page 237



MILAN
◀ 619711CG
4.75"W x 14"H x 5"E
see page 240



MORGAN
◀ 4811PN
◀ 4811BB
5.25"W x 16"H
x 3.75"E
see page 245
ADA



NASH
◀ 613221GM-360
5"W x 16"H x 6.50"E
see page 247



NASH
▶ 613211GM
9.75"W x 15.25"H x 5.50"E
see page 247



NORA
◀ 610311FC
5"W x 17.50"H x 9"E
see page 251



O'NEAL
▲ 3791BB
9.50"W x 7.75"H
x 10.50"E
see page 253



OLIVIA
 ◀ 615011WG-671
 6"W x 14.75"H
 x 6.50"E
 see page 257



OXFORD
 ▶ 619611SP-419
 5"W x 16"H x 5.5"E
 see page 259

PEARSON
 ▼ 4911BI

8.25"W x 11.75"H x 3.25"E
 see page 261
ADA



PORTER
 ▶ 620911RB-425
 5"W x 24"H x 6.25"E
 see page 267

RAVENWOOD
 ▶ 619821BI
 9.75"W x 22"H x 4"E
 see page 270
ADA



REGAN
 ◀ 619411CG-417
 7"W x 24"H x 5.75"E
 see page 276

REID
 ▶ 612011RT
 7"W x 18"H x 4.75"E
 see page 280



RENAISSANCE
 ◀ 621511RN
 9.50"W x 24.75"H
 x 7.50"E
 see page 283

RENAISSANCE
 ▶ 621521RB
 9.50"W x 20.50"H x 4"E
 see page 285
ADA





RIVER CREST
◀ 1907RI-125
13"W x 15"H x 7"E
see page 289



RIVER CREST
◀ 1909RI-125
11.50"W x 33"H x 6"E
see page 289



RIVER CREST
▶ 1908RI-125
9"W x 32"H x 6"E
see page 289



RIVER CREST
◀ 1906RI-125
9"W x 13.50"H x 7"E
see page 289



ROWAN
◀ 611611RT-322
4.50"W x 16"H x 7.50"E
see page 294

SEATON
▶ 610811SF-660
6.75"W x 17"H x 7.50"E
see page 298



SINCLAIR
◀ 617411RB-372
5"W x 20.75"H x 7"E
see page 302

STEELE

- ▶ 8491BB-103
- ▼ 8491BN-103
- ▼ 8491CH-103

6"W x 8"H x 7.25"E
see page 310



STUDIO

- ◀ 1170PN-488
- 8"W x 13.75"H x 4"E
see page 319

ADA



STUDIO

- ◀ 1171PN-489
- 5"W x 13.50"H x 5.50"E
see page 319



STUDIO

- ◀ 1172PN-489
- 12.50"W x 13.50"H
x 5.50"E
see page 319

STELLA

- ▶ 613511BB-326
- ▶ 613511BN-326

5.25"W x 17"H x 5"E
see page 314



VINEYARD

- ◀ 610321FC
- 10"W x 20"H
x 6.75"E
see page 323



WEST PORT

- ◀ 620121OB
- 11"W x 18"H x 6.25"E
see page 327



WESTBROOK

- ▶ 61011BB
- ▶ 61011WG

6.25"W x 18"H
x 4"E

see page 328

ADA



WINDSOR

- ▶ 613811SF-654
- 6"W x 24"H x 7.50"E
see page 333

WYATT

- ▶ 4252SY-000

8"W x 14.50"H x 5"E
see page 338



WYATT

- ◀ 4251SY-000

6"W x 15"H x 5.50"E
see page 338

ZANDER

- ◀ 621931AD

9"W x 20"H x 3.50"E
see page 344

ADA



ZANDER

- ▶ 621931PN

9"W x 20"H x 3.50"E
see page 344

ADA



◀ **4856GR**
Graphite
5"W x 20.25"H
x 6.75"E
Backplate:
4.50"W x .75"H
x 7.50"E
Ctr/Top: 10.25"
2 – 100 Watt
E26 Medium
Finish: GR
Damp Rated



◀ **3711PN-135**
Polished Nickel
▶ **3711BN-135**
Brushed Nickel

6"W x 11.75"H x 7.50"E
Backplate:
5.50"W x 5.50"H x 1"E
Ctr/Top: 2.5"
1 – 100 Watt E26 Medium
Clear Glass
Finishes: BB, BN, GA, PN



◀ **3711BB-135**
Burnished Bronze
◀ **3711GA-135**
Graphite With Aged Brass

6"W x 11.75"H x 7.50"E
Backplate: 5.50"W x 5.50"H x 1"E
Ctr/Top: 2.5"
1 – 100 Watt E26 Medium
Clear Glass
Finishes: BB, BN, GA, PN



▶ **619511OB-654**

Oil Rubbed Bronze
5"W x 20"H x 1"E
Backplate:
20"W x 5"H x 1.50"E
Ctr/Top: 10" Ctr/Btm: 10"
1 - 60 Watt E12 Candelabra
Finish: OB
Damp Rated



◀ **9681BB-AN**

Burnished Bronze
5"W x 14"H x 4"E
Backplate: 4.75"W x
13.75"H x .75"E
Ctr/Top: 7" Ctr/Btm: 7"
1 – 60 Watt E12 Candelabra
Antique Glass
Finish: BB
Damp Rated
ADA



◀ **4191BB**
Burnished Bronze

◀ **4191GR**
Graphite
10"W x 5.75"H x 11.50"E
Backplate: 5"W x 1.75"H x 5"E
Ctr/Top: 5.04"
1 – 75 Watt E26 Medium
Finishes: BB, GR
Damp Rated

▶ **9681PN-CL**

Polished Nickel
5"W x 14"H x 4"E
Backplate: 4.75"W x
13.75"H x .75"E
Ctr/Top: 7" Ctr/Btm: 7"
1 – 60 Watt
E12 Candelabra
Clear Glass
Finish: PN
Damp Rated
ADA



▶ **3787BB**

Burnished Bronze

11"W x 13.75"H x 5.50"E
 Backplate: 6.75"W x 8.5"H x .75"E
 Ctr/Top: 7.75" Ctr/Btm: 4.5"
 2 – 60 Watt E12 Candelabra
 Mist Scavo Glass
 Finish: BB
 Damp Rated



◀ **1701BB-291**

Burnished Bronze

6.50"W x 10.50"H x 7.50"E
 Backplate: 5.75"W x 9.5"H x 1"E
 1 – 100 Watt
 E26 Medium
 Mist Scavo Glass
 Finish: BB
 Damp Rated



▶ **1061CH-142**

Chrome

▶ **1061MN-142**

Matte Nickel

▶ **1061BB-142**

Burnished Bronze

5"W x 10"H x 6.50"E
 Backplate: 5"W x 5"H x 1.25"E
 Ctr/Top: 3" Ctr/Btm: 7"
 1 – 100 Watt E26 Medium
 Acid Washed Glass
 Finishes: BB, CH, MN
 Damp Rated



▶ **8431RM-205**

Raw Umber

5"W x 18"H x 5.50"E
 Backplate: 5.25"W x 7"H x .75"E
 1 – 100 Watt E26 Medium
 Candlelight Glass
 Finish: RM
 Damp Rated



▶ **8511BB-216**

Burnished Bronze

▶ **8511BN-216**

Brushed Nickel

▶ **8511PN-216**

Polished Nickel

5.50"W x 7.50"H x 6"E
 Backplate: 5"W x 6"H x .75"E
 Ctr/Top: 3.25" Ctr/Btm: 4.25"
 1 – 75 Watt E26 Medium
 Soft White Glass
 Finishes: BB, BN, PN
 Damp Rated



◀ **8052SA-558**

Sable

14.75"W x 20"H x 8.5"E
 Backplate: 5.25"W x 5.25"H x 1"E
 Ctr/Top: 17.5" Ctr/Btm: 2.5"
 2 – 60 Watt E12 Candelabra
 Decorative White Fabric
 Stay-Straight Shade
 Finish: SA
 Damp Rated



▶ **8051SA-558**

Sable

5.50"W x 20"H x 7.50"E
 Backplate: 5.25"W x 5.25"H x 1"E
 Ctr/Top: 17.5" Ctr/Btm: 2.5"
 1 – 60 Watt E12 Candelabra
 Decorative White Fabric Stay-Straight Shade
 Finish: SA
 Damp Rated



◀ **1081BB-132**

Burnished Bronze

◀ **1081CH-132**

Chrome

◀ **1081MN-132**

Matte Nickel

5.50"W x 7.50"H x 8"E
 Backplate:
 5.25"W x 7"H x 1"E
 Ctr/Top: 4" Ctr/Btm: 3.5"
 1 – 100 Watt
 E26 Medium
 Acid Washed Glass
 Finishes: BB, CH, MN
 Damp Rated





◀ **8451BB-119**
Burnished Bronze
▶ **8451PN-119**
Polished Nickel
◀ **8451BN-119**
Brushed Nickel

5"W x 8.50"H x 6.50"E
Backplate: 5"W x 5"H x 1"E
Ctr/Top: 6" Ctr/Btm: 2.5"
1 – 75 Watt E26 Medium
Soft White Glass
Finishes: BB, BN, PN
Damp Rated



▶ **1361CH-117**
Chrome
▶ **1361MN-117**
Matte Nickel
▶ **1361BB-117**
Burnished Bronze

5.5"W x 7.25"H x 8"E
Backplate: 5"W x 5"H x 1.5"E
Ctr/Top: 3" Ctr/Btm: 4.25"
1 – 100 Watt E26 Medium
Faux White Alabaster Glass
Finishes: BB, CH, MN
Damp Rated



◀ **1361BB-297**
Burnished Bronze
5.5"W x 7.25"H x 8"E
Backplate: 5"W x 5"H x 1.5"E
Ctr/Top: 3" Ctr/Btm: 4.25"
1 – 100 Watt E26 Medium
Mist Scavo Glass
Finishes: BB
Damp Rated

▶ **1591WB**
Weathered Brown
5.50"W x 11.75"H x 5.50"E
Backplate:
5.5"W x 5.5"H x 1.25"E
Ctr/Top: 7" Ctr/Btm: 4.75"
2 – 60 Watt E26 Medium
Mist Scavo Glass
Finish: WB
Damp Rated



▲ **1680MW**
Matte White
10"W x 5"H x 5"E
Backplate: 10"W x 5"H x 3.75"E
Ctr/ Top: 3.75" Ctr/Btm: 1.25"
1 – 100 Watt E26 Medium
Opal Glass
Finish: MW

▼ **1681MW**
Matte White
10"W x 5"H x 5"E
Backplate: 10"W x 5"H x 3.75"E
Ctr/ Top: 3.75" Ctr/Btm: 1.25"
1 – 100 Watt E26 Medium
Faux White Alabaster Glass
Finish: MW



▲ **1721FF-AL**
Multiple Finishes
14"W x 6"H x 7"E
4.25"W x 5.75"H x 1.5"E
Ctr/Top: 3.25" Ctr/Btm: 2.75"
1 – 100 Watt E26 Medium
Finishes: MN, PB, TS, VB

▼ **1722FF-AL**
Multiple Finishes
12"W x 6"H x 6"E
Backplate:
4.25"W x 5.75"H x 1.5"E
Ctr/Top: 3.25" Ctr/Btm: 2.75"
1 – 100 Watt E26 Medium
Finishes: MN, PB, TS, VB



◀ **1992FF-SW**
Multiple Finishes
11.50"W x 7"H x 4"E
Backplate: 4.5"W x 5.25"H x .75"E
Ctr/Top: 4" Ctr/Btm: 3"
1 – 60 Watt E26 Medium
Soft White Glass
Finishes: BB, MN, PN
Damp Rated
ADA



◀ **1991BB**
Burnished Bronze
11.50"W x 7"H x 4"E
Backplate: 4.5"W x 5.25"H x .75"E
Ctr/Top: 4" Ctr/Btm: 3"
1 – 60 Watt E26 Medium
Mist Scavo Glass
Finish: BB
Damp Rated
ADA

ABELLA

▶ **123031CG-436**

24.25"W x 9.50"H x 6.75"E

see page 15



Install vanity fixtures with glass shades hanging up or down

Dimmable – LED
Dimmer Recommended



ALEXANDER LED

▲ **8072BB-LD**

27.50"W x 5.25"H x 5"E

◀ **8072WG-LD**

27.50"W x 5.25"H x 5"E

see page 25



ALISA

▶ **8022PN-127**

13.50"W x 7.75"H x 6"E

▶ **8023PN-127**

21"W x 7.75"H x 6"E

▶ **8024PN-127**

29.25"W x 7.75"H x 6"E

see page 29





vanity
collection



ALSTON

◀ **121031OB**

24.50"W x 6.25"H x 4.75"E
see page 33



ARDEN

◀ **111231BS-317**

23.50"W x 9"H x 6.75"E

◀ **111221BS-317**

15"W x 9"H x 6.75"E

▼ **111241BS-317**

32"W x 9"H x 6.75"E

see page 37

ASHER

▶ **114921CZ-336**

19.25"W x 10.50"H x 7.50"E

▶ **114931CZ-336**

27"W x 10.50"H x 7.50"E

▼ **114941CZ-336**

36.25"W x 10.50"H x 7.50"E

see page 41



AVANTI

▶ **117621RT-376**
15.50"W x 13"H x 7.50"E

▶ **117631RT-376**
23"W x 13"H x 7.50"E

▶ **117641RT-376**
31"W x 13"H x 7.50"E
see page 44



BARCLAY

◀ **1522CB-287**
20.50"W x 10"H x 9"E

◀ **1523CB-287**
28.25"W x 10"H x 9"E

▼ **1524CB-287**
37.50"W x 10"H x 9"E
see page 59

BAXTER

▶ **8302BB-128**
16.25"W x 11"H x 8"E

▼ **8303BB-128**
24.25"W x 11"H x 8.25"E
see pages 62-63



↑
↓
Install vanity fixtures with glass shades hanging up or down



BAXTER

◀ **8302CH-128**

16.25"W x 11"H x 8"E

▼ **8303CH-128**

24.25"W x 11"H x 8.25"E

see pages 62-63

BAXTER

▶ **8302BN-128**

16.25"W x 11"H x 8"E

▼ **8303BN-128**

24.25"W x 11"H x 8.25"E

see pages 62-63



BAXTER

◀ **8302PN-128**

16.25"W x 11"H x 8"E

▼ **8303PN-128**

24.25"W x 11"H x 8.25"E

see pages 62-63



Install vanity fixtures with glass shades hanging up or down



BELMONT

▲ 1332BB-287

17"W x 9.50"H x 6.50"E

▲ 1333BB-287

25"W x 9.50"H x 6.50"E

◀ 1334BB-287

34"W x 9.50"H x 6.50"E

see page 67

BELMONT

▶ 1332BB-242

17"W x 9.50"H x 6.50"E

▶ 1333BB-242

25"W x 9.50"H x 6.50"E

▼ 1334BB-242

34"W x 9.50"H x 6.50"E

see page 67



BERKELEY

◀ 8533WG-300

20.75"W x 8"H x 7.50"E

◀ 8532WG-300

13.75"W x 8"H x 6.75"E

▼ 8534WG-300

29.50"W x 8"H x 7.50"E

see page 70





BLAIR

◀ **8553AS-299**
20"W x 9.25"H x 7"E

◀ **8552AS-299**
17.75"W x 9"H x 6.75"E

▼ **8554AS-299**
27"W x 9"H x 7.25"E
see page 75



BLAKELY

▶ **8522AS-114**
15.75"W x 8.75"H x 7.75"E

▶ **8523AS-114**
24.25"W x 8.75"H x 7.75"E

▶ **8523AG-114**
24.25"W x 8.75"H x 7.75"E

▶ **8523CG-114**
24.25"W x 8.75"H x 7.75"E

▶ **8524AS-114**
33"W x 8.75"H x 7.75"E
see page 83



BLAKELY

◀ **8524AS-CR**
29.50"W x 10"H x 6"E

◀ **8523AS-CR**
20.50"W x 10"H x 6"E

▼ **8528AS-CR**
18.50"W x 9.50"H x 6"E

▼ **8522AS-CR**
12"W x 10"H x 6"E
see pages 84-85

BLAKELY

▶ **8524AG-CR**
29.50"W x 10"H x 6"E

▶ **8522AG-CR**
12"W x 10"H x 6"E

▶ **8528AG-CR**
18.50"W x 9.50"H x 6"E

▶ **8523AG-CR**
20.50"W x 10"H x 6"E
see pages 84-85



BLAKELY

▶ **8524CG-CR**
29.50"W x 10"H x 6"E

▶ **8522CG-CR**
12"W x 10"H x 6"E

▶ **8528CG-CR**
18.50"W x 9.50"H x 6"E

▶ **8523CG-CR**
20.50"W x 10"H x 6"E
see pages 84-85



BODEN

▶ **112341BB-324**
32"W x 10.50"H x 6"E

▼ **112321BB-324**
14"W x 10.50"H x 6"E

▼ **112331BB-324**
23"W x 10.50"H x 6"E
see pages 88-89





BODEN

◀ **112341BN-324**
32"W x 10.50"H x 6"E

◀ **112321BN-324**
14"W x 10.50"H x 6"E

▼ **112331BN-324**
23"W x 10.50"H x 6"E
see pages 88-89

BODEN

▶ **112321SF-324**
14"W x 10.50"H x 6"E

▶ **112331SF-324**
23"W x 10.50"H x 6"E

▼ **112341SF-324**
32"W x 10.50"H x 6"E
see pages 88-89



CAMDEN

◀ **120731PN-423**
23.50"W x 9.25"H x 6.50"E

◀ **120721PN-423**
13.75"W x 9.25"H x 6.50"E

▼ **120741PN-423**
33.25"W x 9.25"H x 6.50"E
see page 96



CARLYLE

▲ **111721GS-352**
15"W x 7.25"H x 7"E

◀ **111731GS-352**
24"W x 7.25"H x 7"E

▼ **111741GS-352**
32.75"W x 7.25"H x 7"E
see page 103



CHANDLER

◀ **1803MN-222**
33"W x 10.25"H x 10"E

◀ **1803BB-292**
33"W x 10.25"H x 10"E

◀ **1804MN-222**
43.50"W x 10.25"H x 10"E

▼ **1804BB-292**
43.50"W x 10.25"H x 10"E
see page 113



CHAPMAN
◀ **8402BB-201**
16"W x 9"H x 7.50"E

◀ **8404BB-201**
32"W x 9"H x 7.50"E

◀ **8403BB-201**
24"W x 9"H x 7.50"E
see pages 118-119



CHAPMAN
▶ **8402BB-202**
16"W x 9"H x 7.50"E

▶ **8403BB-202**
24"W x 9"H x 7.50"E

▼ **8404BB-202**
32"W x 9"H x 7.50"E
see pages 118-119



CHAPMAN
◀ **8402MN-202**
16"W x 9"H x 7.50"E

◀ **8403MN-202**
24"W x 9"H x 7.50"E

▼ **8404MN-202**
32"W x 9"H x 7.50"E
see pages 118-119



COLE

▶ **121321AO-427**
14.50"W x 11.75"H x 6.25"E

▶ **121331AO-427**
24"W x 11.75"H x 6.25"E

▶ **121341AO-427**
33"W x 11.75"H x 6.25"E
see page 137



CORRIGAN

▼ **110931AS-315**
22.50"W x 8"H x 7.25"E
see page 140



CORRIGAN

▲ **110921AS-315**
14"W x 8"H x 7.25"E



COVINGTON

◀ **8442AN-102**
▼ **8442BB-102**
12.50"W x 9"H x 6.25"E
see page 145



COVINGTON

◀ **8443AN-102**
◀ **8443BB-102**
19.25"W x 9"H x 6.25"E
see page 145





DAWSON

◀ **119331AD-674**
25.50"W x 12"H x 7.25"E

◀ **119321AD-674**
16"W x 12"H x 7.25"E

▼ **119341AD-674**
35.25"W x 12"H x 7.25"E
see page 149

EMERY

▶ **8042BN-150**
8.50"W x 9.75"H x 4"E

ADA

▶ **8043BN-150**
14.50"W x 9.75"H x 4"E

ADA

▶ **8044BN-150**
21.75"W x 9.75"H x 4"E

ADA

see page 159



EVERLEIGH

▶ **117721FG-303**
17.25"W x 11.50"H x 7"E

▶ **117731FG-303**
25.50"W x 11.50"H x 7"E

▶ **117741FG-303**
38.50"W x 11.50"H x 7"E
see page 162



FIFTH AVENUE

▶ **1067WG-101**

14.25"W x 10"H x 8"E


▶ **1068WG-101**

23.25"W x 10"H x 8"E

▼ **1069WG-101**

32.50"W x 10"H x 8"E

see page 167



GAVIN

◀ **121461IG**

21.75"W x 8.25"H x 4.50"E

▼ **121481IG**

30"W x 8.25"H x 4.50"E

see page 176



HILL HOUSE

◀ **1883BB-252**

23.50"W x 11"H x 7"E

◀ **1882BB-252**

18"W x 11"H x 7"E


▼ **1884BB-252**

31"W x 11"H x 7"E

see page 183

↑
↓
Install vanity fixtures with glass shades hanging up or down

JACKSON
▶ **4893OR**
19.75"W x 8"H x 4.75"E
see page 190



KINGSLEY
◀ **118731DS-299**
23"W x 9"H x 7.75"E
◀ **118721DS-299**
14.75"W x 9"H x 7.75"E
▼ **118741DS-299**
31.50"W x 9"H x 7.75"E
see page 194



KNOX
◀ **120331OB-435**
25"W x 8.75"H x 7"E
see page 198

LEIGH
▶ **8113BB-300**
22.50"W x 9.50"H x 6.25"E
see page 203



↑
↔
↓
Install vanity fixtures with glass shades hanging up or down



LUNA

▶ **1008WG-410**
26.50"W x 8.50"H x 8.75"E

▶ **1007WG-410**
17"W x 8.50"H x 8.75"E

▶ **1009WG-410**
36.25"W x 8.50"H x 8.75"E
see page 211



MID-CENTURY

◀ **121141AD-426**
32"W x 9.75"H x 6.75"E

◀ **121131AD-426**
23.50"W x 9.75"H x 6.75"E

▼ **121121AD-426**
14.50"W x 9.75"H x 6.75"E
see page 225

MID-CENTURY

▶ **121131PN-426**
23.50"W x 9.75"H x 6.75"E

▶ **121121PN-426**
14.50"W x 9.75"H x 6.75"E

▼ **121141PN-426**
32"W x 9.75"H x 6.75"E
see page 225



MIDTOWN

▶ **1237BB-450**

17.50"W x 13.50"H x 7.50"E

▶ **1238BB-450**

25.50"W x 13.50"H x 7.50"E

▼ **1239BB-450**

35"W x 13.50"H x 7.50"E

see page 235



MIDTOWN

◀ **1237BB-451**

17.50"W x 13.50"H x 7.50"E

◀ **1238BB-451**

25.50"W x 13.50"H x 7.50"E

▼ **1239BB-451**

35"W x 13.50"H x 7.50"E

see page 234



MIDTOWN

▶ **1237PN-451**

17.50"W x 13.50"H x 7.50"E

▶ **1238PN-451**

25.50"W x 13.50"H x 7.50"E

▼ **1239PN-451**

35"W x 13.50"H x 7.50"E

see page 237





MIDTOWN
 ◀ 1237MN-451
 17.50"W x 13.50"H x 7.50"E
 ◀ 1238MN-451
 25.50"W x 13.50"H x 7.50"E
 ▼ 1239MN-451
 35"W x 13.50"H x 7.50"E
 see page 236



O'NEAL
 ◀ 3792BB
 19.75"W x 7.75"H x 10.50"E
 ▼ 3793BB
 30"W x 7.75"H x 10.50"E
 see page 253

OLIVIA

▶ 115021WG-375
 17"W x 10.50"H x 6.25"E

▶ 115031WG-375
 23.75"W x 10.50"H x 6.25"E

▶ 115041WG-375
 32.50"W x 10.50"H x 6.25"E
 see page 257





OXFORD

◀ **119631SP-419**

22"W x 9.25"H x 6.50"E

see page 259

PORTER

▶ **120941RB-425**

33.50"W x 9"H x 6.75"E

▶ **120921RB-425**

14.25"W x 9"H x 6.75"E

▶ **120931RB-425**

24"W x 9"H x 6.75"E

see page 266



RAVENWOOD

◀ **119821BI-435**

13.25"W x 9.50"H x 5.50"E

◀ **119831BI-435**

23"W x 9.50"H x 5.50"E

▼ **119841BI-435**

32.75"W x 9.50"H x 5.50"E

see page 271



REGAN LED

▶ **119421CG-418-LD**
13.25"W x 9.50"H x 5.50"E

▶ **119431CG-418-LD**
23.50"W x 7.50"H x 7"E

▼ **119441CG-418-LD**
32.75"W x 9.50"H x 5.50"E
see page 277

**Dimmable – LED
Dimmer Recommended**



REID

◀ **112031RT-323**
23.75"W x 8.25"H x 7.50"E

◀ **112021RT-323**
17.50"W x 8.25"H x 7.50"E

▼ **112041RT-323**
23.75"W x 8.25"H x 10.50"E
see page 281

RENAISSANCE

▶ **121531RN-428**
25"W x 9.50"H x 6.75"E

▶ **121541RN-428**
35"W x 9.50"H x 6.75"E
see page 284



↑
↓
Install vanity fixtures with glass shades hanging up or down

RIVER CREST

▶ **1903RI-125**

29"W x 11.50"H x 7.50"E

see page 289



ROWAN

▶ **111631RT-322**

22"W x 10"H x 7.25"E

▶ **111621RT-322**

13.75"W x 10"H x 7.25"E

▼ **111641RT-322**

30.25"W x 10"H x 7.25"E

see page 295



SEATON

▶ **110821SF-302**

17"W x 11.25"H x 5.75"E

▶ **110831SF-302**

26.50"W x 11.25"H x 5.75"E

▼ **110841SF-302**

34"W x 11.25"H x 5.75"E

see page 299



SINCLAIR

▶ **117421RB-372**
14"W x 8.50"H x 6.25"E

▶ **117431RB-372**
23.25"W x 8.50"H x 6.25"E

▼ **117441RB-372**
32.50"W x 8.50"H x 6.25"E
see page 303



STEELE

◀ **8492CH-103**
14.75"W x 8"H x 7.25"E

◀ **8493CH-103**
23.25"W x 8"H x 7.25"E

▼ **8494CH-103**
32"W x 8"H x 7.25"E
see pages 312-313

STEELE

▶ **8492BB-103**
14.75"W x 8"H x 7.25"E

▶ **8493BB-103**
23.25"W x 8"H x 7.25"E

▼ **8494BB-103**
32"W x 8"H x 7.25"E
see pages 312-313





STEELE

◀ **8493BN-103**
23.25"W x 8"H x 7.25"E

◀ **8492BN-103**
14.75"W x 8"H x 7.25"E

▼ **8494BN-103**
32"W x 8"H x 7.25"E
see pages 312-313

STUDIO

▶ **1398PN-105**
20.25"W x 10.50"H x 6.50"E

▶ **1397PN-105**
13"W x 10.50"H x 6.50"E

▼ **1399PN-105**
28.25"W x 10.50"H x 6.50"E
see page 318



WYATT

◀ **8012SY-123**
17"W x 8.50"H x 8"E

◀ **8013SY-123**
25.50"W x 8.50"H x 9.50"E

◀ **8014SY-123**
32.25"W x 8.50"H x 9.50"E
see page 341

► **121821AD-432**

Aged Brass
 14"W x 10"H x 7.25"E
 Backplate: 5"W x 5"H x .75"E
 Ctr/Top: 2" Ctr/Btm: 8"
 2 – 100 Watt E26 Medium
 Clear Glass
 Finishes: AD, OB, PN
 Damp Rated



◄ **121841AD-432**

Aged Brass
 33"W x 10"H x 7.25"E
 Backplate: 5"W x 5"H x .75"E
 Ctr/Top: 2" Ctr/Btm: 8"
 4 – 100 Watt E26 Medium
 Clear Glass
 Finishes: AD, OB, PN
 Damp Rated

▲ **121831AD-432**

Aged Brass
 23"W x 10"H x 7.25"E
 Backplate: 5"W x 5"H x 1"E
 Ctr/Top: 2.75" Ctr/Btm: 8"
 3 – 100 Watt E26 Medium
 Clear Glass
 Finishes: AD, OB, PN
 Damp Rated



◄ **121821PN-432**

Polished Nickel
 14"W x 10"H x 7.25"E
 Backplate: 5"W x 5"H x .75"E
 Ctr/Top: 8" Ctr/Btm: 2"
 2 – 100 Watt E26 Medium
 Clear Glass
 Finishes: AD, OB, PN
 Damp Rated

▲ **121831PN-432**

Polished Nickel
 23"W x 10"H x 7.25"E
 Backplate:
 5"W x 5"H x 1"E
 Ctr/Top: 2" Ctr/Btm: 8"
 3 – 100 Watt E26 Medium
 Clear Glass
 Finishes: AD, OB, PN
 Damp Rated

► **121841PN-432**

Polished Nickel
 33"W x 10"H x 7.25"E
 Backplate:
 5"W x 5"H x .75"E
 Ctr/Top: 2" Ctr/Btm: 8"
 4 – 100 Watt E26 Medium
 Clear Glass
 Finishes: AD, OB, PN
 Damp Rated



► **121821OB-432**

Old Bronze
 14"W x 10"H x 7.25"E
 Backplate: 5"W x 5"H x .75"E
 Ctr/Top: 2" Ctr/Btm: 8"
 2 – 100 Watt E26 Medium
 Clear Glass
 Finishes: AD, OB, PN
 Damp Rated



◄ **121841OB-432**

Old Bronze
 33"W x 10"H x 7.25"E
 Backplate: 5"W x 5"H x .75"E
 Ctr/Top: 2" Ctr/Btm: 8"
 4 – 100 Watt E26 Medium
 Clear Glass
 Finishes: AD, OB, PN
 Damp Rated

▲ **121831OB-432**

Old Bronze
 23"W x 10"H x 7.25"E
 Backplate: 5"W x 5"H x 1"E
 Ctr/Top: 2.75" Ctr/Btm: 8"
 3 – 100 Watt E26 Medium
 Clear Glass
 Finishes: AD, OB, PN
 Damp Rated

▶ **121721PN-431**

Polished Nickel
 14.75"W x 9.50"H x 7.25"E
 Backplate: 10"W x 4.50"H x .75"E
 Ctr/Top: 2" Ctr/Btm: 7.50"
 2 – 100 Watt E26 Medium
 Clear Glass
 Finishes: BN, OB, PN
 Damp Rated



◀ **121741PN-431**

Polished Nickel
 32.50"W x 9.50"H x 7.25"E
 Backplate:
 10"W x 4.50"H x .75"E
 Ctr/Top: 2" Ctr/Btm: 7.50"
 4 – 100 Watt E26 Medium
 Clear Glass
 Finishes: BN, OB, PN
 Damp Rated

▲ **121731PN-431**

Polished Nickel
 23.50"W x 9.50"H x 7.25"E
 Backplate:
 10"W x 4.50"H x .75"E
 Ctr/Top: 2" Ctr/Btm: 7.50"
 3 – 100 Watt E26 Medium
 Clear Glass
 Finishes: BN, OB, PN
 Damp Rated



▼ **121741BN-431**

Brushed Nickel
 32.50"W x 9.50"H x 7.25"E
 Backplate:
 10"W x 4.50"H x .75"E
 Ctr/Top: 2" Ctr/Btm: 7.50"
 4 – 100 Watt E26 Medium
 Clear Glass
 Finishes: BN, OB, PN
 Damp Rated

▲ **121721BN-431**

Brushed Nickel
 14.75"W x 9.50"H x 7.25"E
 Backplate:
 10"W x 4.50"H x .75"E
 Ctr/Top: 2" Ctr/Btm: 7.50"
 2 – 100 Watt E26 Medium
 Clear Glass
 Finishes: BN, OB, PN
 Damp Rated

▲ **121731BN-431**

Brushed Nickel
 23.50"W x 9.50"H x 7.25"E
 Backplate:
 10"W x 4.50"H x .75"E
 Ctr/Top: 2" Ctr/Btm: 7.50"
 3 – 100 Watt E26 Medium
 Clear Glass
 Finishes: BN, OB, PN
 Damp Rated



▶ **121721OB-431**

Old Bronze
 14.75"W x 9.50"H x 7.25"E
 Backplate: 10"W x 4.50"H x .75"E
 Ctr/Top: 2" Ctr/Btm: 7.50"
 2 – 100 Watt E26 Medium
 Clear Glass
 Finishes: BN, OB, PN
 Damp Rated



◀ **121741OB-431**

Old Bronze
 32.50"W x 9.50"H x 7.25"E
 Backplate:
 10"W x 4.50"H x .75"E
 Ctr/Top: 2" Ctr/Btm: 7.50"
 4 – 100 Watt E26 Medium
 Clear Glass
 Finishes: BN, OB, PN
 Damp Rated

▲ **121731OB-431**

Old Bronze
 23.50"W x 9.50"H x 7.25"E
 Backplate:
 10"W x 4.50"H x .75"E
 Ctr/Top: 2" Ctr/Btm: 7.50"
 3 – 100 Watt E26 Medium
 Clear Glass
 Finishes: BN, OB, PN
 Damp Rated



◀ **120521CG-422**

Capital Gold
 13.25"W x 9"H x 6.25"E
 Backplate: 5"W x 5"H x .75"E
 Ctr/Top: 2.25" Ctr/Btm: 6.75"
 2 – 100 Watt E26 Medium
 Clear Ice Glass
 Finish: CG
 Damp Rated

▲ **120531CG-422**

Capital Gold
 23"W x 9"H x 6.25"E
 Backplate:
 5"W x 5"H x .75"E
 Ctr/Top: 2.25"
 Ctr/Btm: 6.75"
 3 – 100 Watt
 E26 Medium
 Clear Ice Glass
 Finish: CG
 Damp Rated

▶ **120541CG-422**

Capital Gold
 33"W x 9"H x 6.25"E
 Backplate:
 5"W x 5"H x .75"E
 Ctr/Top: 2.25"
 Ctr/Btm: 6.75"
 4 – 100 Watt
 E26 Medium
 Clear Ice Glass
 Finish: CG
 Damp Rated





▲ **8513BB-216**

Burnished Bronze

21"W x 6.75"H x 6.75"E
 Backplate: 6"W x 5"H x .75"E
 Ctr/Top: 2.50" Ctr/Btm: 4.25"
 3 – 75 Watt E26 Medium
 Soft White Glass
 Finishes: BB, BN, PN
 Damp Rated

▶ **8514BB-216**

Burnished Bronze

28.75"W x 6.75"H x 6.75"E
 Backplate: 6"W x 5"H x .75"E
 Ctr/Top: 2.50" Ctr/Btm: 4.25"
 4 – 75 Watt E26 Medium
 Soft White Glass
 Finishes: BB, BN, PN
 Damp Rated



◀ **8512BB-216**

Burnished Bronze

13.25"W x 6.75"H x 6.75"E
 Backplate: 6"W x 5"H x .75"E
 Ctr/Top: 4.25" Ctr/Btm: 2.50"
 2 – 75 Watt E26 Medium
 Soft White Glass
 Finishes: BB, BN, PN
 Damp Rated



▲ **8513BN-216**

Brushed Nickel

21"W x 6.75"H x 6.75"E
 Backplate: 6"W x 5"H x .75"E
 Ctr/Top: 2.50" Ctr/Btm: 4.25"
 3 – 75 Watt E26 Medium
 Soft White Glass
 Finishes: BB, BN, PN
 Damp Rated

▶ **8514BN-216**

Brushed Nickel

28.75"W x 6.75"H x 6.75"E
 Backplate: 6"W x 5"H x .75"E
 Ctr/Top: 2.50" Ctr/Btm: 4.25"
 4 – 75 Watt E26 Medium
 Soft White Glass
 Finishes: BB, BN, PN
 Damp Rated



◀ **8512BN-216**

Brushed Nickel

13.25"W x 6.75"H x 6.75"E
 Backplate: 6"W x 5"H x .75"E
 Ctr/Top: 4.25" Ctr/Btm: 2.50"
 2 – 75 Watt E26 Medium
 Soft White Glass
 Finishes: BB, BN, PN
 Damp Rated



▲ **8513PN-216**

Polished Nickel

21"W x 6.75"H x 6.75"E
 Backplate: 6"W x 5"H x .75"E
 Ctr/Top: 2.50" Ctr/Btm: 4.25"
 3 – 75 Watt E26 Medium
 Soft White Glass
 Finishes: BB, BN, PN
 Damp Rated

▶ **8514PN-216**

Polished Nickel

28.75"W x 6.75"H x 6.75"E
 Backplate: 6"W x 5"H x .75"E
 Ctr/Top: 2.50" Ctr/Btm: 4.25"
 4 – 75 Watt E26 Medium
 Soft White Glass
 Finishes: BB, BN, PN
 Damp Rated



◀ **8512PN-216**

Polished Nickel

13.25"W x 6.75"H x 6.75"E
 Backplate: 6"W x 5"H x .75"E
 Ctr/Top: 4.25" Ctr/Btm: 2.50"
 2 – 75 Watt E26 Medium
 Soft White Glass
 Finishes: BB, BN, PN
 Damp Rated





▲ **8344BN-155**

Brushed Nickel

36"W x 7.25"H x 5"E

Backplate:

6.25"W x 4.50"H x .75"E

Ctr/Top: 5" Ctr/Btm: 2.25"

4 – 60 Watt E12 Candelabra

Milk Glass

Finish: BN

Damp Rated

▶ **8342BN-155**

Brushed Nickel

16"W x 7.25"H x 5"E

Backplate:

6.25"W x 4.50"H x .75"E

Ctr/Top: 5" Ctr/Btm: 2.25"

2 – 60 Watt E12 Candelabra

Milk Glass

Finish: BN

Damp Rated



◀ **8343BN-155**

Brushed Nickel

26"W x 7.25"H x 5"E

Backplate: 6.25"W x 4.50"H x .75"E

Ctr/Top: 2.25" Ctr/Btm: 5"

3 – 60 Watt E12 Candelabra

Milk Glass

Finish: BN

Damp Rated



◀ **8033GR**

Graphite

22"W x 8.50"H x 6.25"E

Backplate: 8"W x 4.75"H x .75"E

Ctr/Top: 6.25" Ctr/Btm: 2.25"

3 – 100 Watt E26 Medium

Clear Glass

Finish: GR

Damp Rated





▼ **1703BB-291**

Burnished Bronze

31"W x 11.25"H x 8"E

Backplate: 9.50"W x 5.75"H x 1"E

Ctr/Top: 3.75" Ctr/Btm: 7.75"

3 – 100 Watt E26 Medium

Mist Scavo Glass

Finish: BB

Damp Rated

▲ **1702BB-291**

Burnished Bronze

22.50"W x 10.75"H x 7.50"E

Backplate: 9.50"W x 5.75"H x 1"E

Ctr/Top: 3.25" Ctr/Btm: 7.75"

2 – 100 Watt E26 Medium

Mist Scavo Glass

Finish: BB

Damp Rated



▲ **1737WG-122**

Winter Gold

16.75"W x 10"H x 6.50"E

Backplate:

7"W x 5.25"H x 1"E

Ctr/Top: 7.50" Ctr/Btm: 2.50"

2 – 100 Watt E26 Medium

Soft White Glass

Finish: WG

Damp Rated

▶ **1738WG-122**

Winter Gold

23.25"W x 10"H x 6.50"E

Backplate: 7"W x 5.25"H x 1"E

Ctr/Top: 2.50" Ctr/Btm: 7.50"

3 – 100 Watt E26 Medium

Soft White Glass

Finish: WG

Damp Rated



↑
↓
Install vanity fixtures with glass shades hanging up or down

▶ **1739WG-122**

Winter Gold

31.50"W x 10"H x 6.50"E

Backplate:

7"W x 5.25"H x 1"E

Ctr/Top: 2.50" Ctr/Btm: 7.50"

4 – 100 Watt E26 Medium

Soft White Glass

Finish: WG

Damp Rated





◀ **8452BB-119**
Burnished Bronze
 12.50"W x 8.50"H x 6.50"E
 Backplate: 5"W x 5"H x 1"E
 Ctr/Top: 2.50" Ctr/Btm: 6"
 2 – 75 Watt E26 Medium
 Soft White Glass
 Finishes: BB, BN, PN
 Damp Rated



◀ **8454BB-119**
Burnished Bronze
 27"W x 8.50"H x 6.50"E
 Backplate: 5"W x 5"H x 1"E
 Ctr/Top: 2.50" Ctr/Btm: 6"
 4 – 75 Watt E26 Medium
 Soft White Glass
 Finishes: BB, BN, PN
 Damp Rated

▲ **8453BB-119**
Burnished Bronze
 20"W x 8.50"H x 6.50"E
 Backplate: 5"W x 5"H x 1"E
 Ctr/Top: 2.50" Ctr/Btm: 6"
 3 – 75 Watt E26 Medium
 Soft White Glass
 Finishes: BB, BN, PN
 Damp Rated



▲ **8453BN-119**
Polished Nickel
 20"W x 8.50"H x 6.50"E
 Backplate: 5"W x 5"H x 1"E
 Ctr/Top: 2.50" Ctr/Btm: 6"
 3 – 75 Watt E26 Medium
 Soft White Glass
 Finishes: BB, BN, PN
 Damp Rated

▶ **8454PN-119**
Polished Nickel
 27"W x 8.50"H x 6.50"E
 Backplate: 5"W x 5"H x 1"E
 Ctr/Top: 2.50" Ctr/Btm: 6"
 4 – 75 Watt E26 Medium
 Soft White Glass
 Finishes: BB, BN, PN
 Damp Rated

▶ **8452PN-119**
Polished Nickel
 12.50"W x 8.50"H x 6.50"E
 Backplate: 5"W x 5"H x 1"E
 Ctr/Top: 2.50" Ctr/Btm: 6"
 2 – 75 Watt E26 Medium
 Soft White Glass
 Finishes: BB, BN, PN
 Damp Rated




◀ **8452BN-119**
Brushed Nickel
 12.50"W x 8.50"H x 6.50"E
 Backplate: 5"W x 5"H x 1"E
 Ctr/Top: 2.50" Ctr/Btm: 6"
 2 – 75 Watt E26 Medium
 Soft White Glass
 Finishes: BB, BN, PN
 Damp Rated



◀ **8454BN-119**
Brushed Nickel
 27"W x 8.50"H x 6.50"E
 Backplate: 5"W x 5"H x 1"E
 Ctr/Top: 2.50" Ctr/Btm: 6"
 4 – 75 Watt E26 Medium
 Soft White Glass
 Finishes: BB, BN, PN
 Damp Rated

▲ **8453BN-119**
Brushed Nickel
 20"W x 8.50"H x 6.50"E
 Backplate: 5"W x 5"H x 1"E
 Ctr/Top: 2.50" Ctr/Btm: 6"
 3 – 75 Watt E26 Medium
 Soft White Glass
 Finishes: BB, BN, PN
 Damp Rated



▲ **1062MN-142**
Matte Nickel
 14"W x 10"H x 6.50"E
 Backplate: 5"W x 5"H x 1.25"E
 Ctr/Top: 3" Ctr/Btm: 7"
 2 – 100 Watt E26 Medium
 Acid Washed Glass
 Finishes: BB, CH, MN
 Damp Rated



▲ **1063MN-142**
Matte Nickel
 20.75"W x 10"H x 6.50"E
 Backplate: 5"W x 5"H x 1.25"E
 Ctr/Top: 3" Ctr/Btm: 7"
 3 – 100 Watt E26 Medium
 Acid Washed Glass
 Finishes: BB, CH, MN
 Damp Rated

▼ **1064MN-142**
Matte Nickel
 28.50"W x 10"H x 6.50"E
 Backplate: 5"W x 5"H x 1.25"E
 Ctr/Top: 3" Ctr/Btm: 7"
 4 – 100 Watt E26 Medium
 Acid Washed Glass
 Finishes: BB, CH, MN
 Damp Rated



▼ **1064CH-142**
Chrome
 28.50"W x 10"H x 6.50"E
 Backplate: 5"W x 5"H x 1.25"E
 Ctr/Top: 3" Ctr/Btm: 7"
 4 – 100 Watt E26 Medium
 Acid Washed Glass
 Finishes: BB, CH, MN
 Damp Rated



▲ **1063CH-142**
Chrome
 20.75"W x 10"H x 6.50"E
 Backplate: 5"W x 5"H x 1.25"E
 Ctr/Top: 3" Ctr/Btm: 7"
 3 – 100 Watt E26 Medium
 Acid Washed Glass
 Finishes: BB, CH, MN
 Damp Rated



▲ **1062CH-142**
Chrome
 14"W x 10"H x 6.50"E
 Backplate: 5"W x 5"H x 1.25"E
 Ctr/Top: 3" Ctr/Btm: 7"
 2 – 100 Watt E26 Medium
 Acid Washed Glass
 Finishes: BB, CH, MN
 Damp Rated



▲ **1062BB-142**
Burnished Bronze
 14"W x 10"H x 6.50"E
 Backplate: 5"W x 5"H x 1.25"E
 Ctr/Top: 3" Ctr/Btm: 7"
 2 – 100 Watt E26 Medium
 Acid Washed Glass
 Finishes: BB, CH, MN
 Damp Rated



▲ **1063BB-142**
Burnished Bronze
 20.75"W x 10"H x 6.50"E
 Backplate: 5"W x 5"H x 1.25"E
 Ctr/Top: 3" Ctr/Btm: 7"
 3 – 100 Watt E26 Medium
 Acid Washed Glass
 Finishes: BB, CH, MN
 Damp Rated

▼ **1064BB-142**
Burnished Bronze
 28.50"W x 10"H x 6.50"E
 Backplate: 5"W x 5"H x 1.25"E
 Ctr/Top: 3" Ctr/Btm: 7"
 4 – 100 Watt E26 Medium
 Acid Washed Glass
 Finishes: BB, CH, MN
 Damp Rated





▲ **1792MN-223**
Matte Nickel
 16.75"W x 8.75"H x 9"E
 Backplate: 9"W x 5"H x 1"E
 Ctr/Top: 6" Ctr/Btm: 2.75"
 2 – 100 Watt E26 Medium
 White Faux Alabaster Glass
 Finish: MN
 Damp Rated



▶ **1794MN-223**
Matte Nickel
 33.50"W x 8.75"H x 9"E
 Backplate: 9"W x 5"H x 1"E
 Ctr/Top: 6" Ctr/Btm: 2.75"
 4 – 100 Watt E26 Medium
 White Faux Alabaster Glass
 Finish: MN
 Damp Rated

◀ **1793MN-223**
Matte Nickel
 25"W x 8.75"H x 9"E
 Backplate: 9"W x 5"H x 1"E
 Ctr/Top: 6" Ctr/Btm: 2.75"
 3 – 100 Watt E26 Medium
 White Faux Alabaster Glass
 Finish: MN
 Damp Rated



▶ **1793CH-219**
Chrome
 25"W x 8.75"H x 9"E
 Backplate: 9"W x 5"H x 1"E
 Ctr/Top: 6" Ctr/Btm: 2.75"
 3 – 100 Watt E26 Medium
 Soft White Glass
 Finish: CH
 Damp Rated



◀ **1794CH-219**
Chrome
 33.50"W x 8.75"H x 9"E
 Backplate:
 9"W x 5"H x 1"E
 Ctr/Top: 6" Ctr/Btm: 2.75"
 4 – 100 Watt E26 Medium
 Soft White Glass
 Finish: CH
 Damp Rated

▲ **1792CH-219**
Chrome
 16.75"W x 8.75"H x 9"E
 Backplate:
 9"W x 5"H x 1"E
 Ctr/Top: 6" Ctr/Btm: 2.75"
 2 – 100 Watt E26 Medium
 Soft White Glass
 Finish: CH
 Damp Rated



▲ **1792BB-293**
Burnished Bronze
 16.75"W x 8.75"H x 9"E
 Backplate: 9"W x 5"H x 1"E
 Ctr/Top: 6" Ctr/Btm: 2.75"
 2 – 100 Watt E26 Medium
 Mist Scavo Glass
 Finish: BB
 Damp Rated



▶ **1794BB-293**
Burnished Bronze
 33.50"W x 8.75"H x 9"E
 Backplate: 9"W x 5"H x 1"E
 Ctr/Top: 6" Ctr/Btm: 2.75"
 4 – 100 Watt E26 Medium
 Mist Scavo Glass
 Finish: BB
 Damp Rated

◀ **1793BB-293**
Burnished Bronze
 25"W x 8.75"H x 9"E
 Backplate: 9"W x 5"H x 1"E
 Ctr/Top: 6" Ctr/Btm: 2.75"
 3 – 100 Watt E26 Medium
 Mist Scavo Glass
 Finish: BB
 Damp Rated





▲ **1087CH-132**

Chrome
 12.50"W x 7"H x 8"E
 Backplate: 7"W x 5.25"H x 1"E
 Ctr/Top: 3.25" Ctr/Btm: 3.75"
 2 – 100 Watt E26 Medium
 Acid Washed Glass
 Finishes: BB, CH, MN
 Damp Rated

↑
 ↓
 Install vanity fixtures with glass shades hanging up or down

▼ **1088CH-132**

Chrome
 18"W x 7"H x 7.50"E
 Backplate: 7"W x 5.25"H x 1"E
 Ctr/Top: 3.25" Ctr/Btm: 3.75"
 3 – 100 Watt E26 Medium
 Acid Washed Glass
 Finishes: BB, CH, MN
 Damp Rated



▶ **1087BB-132**

Burnished Bronze
 12.50"W x 7"H x 8"E
 Backplate: 7"W x 5.25"H x 1"E
 Ctr/Top: 3.25" Ctr/Btm: 3.75"
 2 – 100 Watt E26 Medium
 Acid Washed Glass
 Finishes: BB, CH, MN
 Damp Rated



◀ **1088BB-132**

Burnished Bronze
 18"W x 7"H x 7.50"E
 Backplate: 7"W x 5.25"H x 1"E
 Ctr/Top: 3.25" Ctr/Btm: 3.75"
 3 – 100 Watt E26 Medium
 Acid Washed Glass
 Finishes: BB, CH, MN
 Damp Rated



▼ **1088MN-132**

Matte Nickel
 18"W x 7"H x 7.50"E
 Backplate: 7"W x 5.25"H x 1"E
 Ctr/Top: 3.25" Ctr/Btm: 3.75"
 3 – 100 Watt E26 Medium
 Acid Washed Glass
 Finishes: BB, CH, MN
 Damp Rated



▲ **1087MN-132**

Matte Nickel
 12.50"W x 7"H x 8"E
 Backplate: 7"W x 5.25"H x 1"E
 Ctr/Top: 3.25" Ctr/Btm: 3.75"
 2 – 100 Watt E26 Medium
 Acid Washed Glass
 Finishes: BB, CH, MN
 Damp Rated





▲ **1082CH-132**
Chrome
 12"W x 9.50"H x 6"E
 Backplate: 7"W x 5.25"H x 1"E
 Ctr/Top: 2.75" Ctr/Btm: 6.75"
 2 – 100 Watt E26 Medium
 Acid Washed Glass
 Finishes: BB, CH, MN
 Damp Rated



▲ **1083CH-132**
Chrome
 16.75"W x 9.50"H x 6"E
 Backplate: 7"W x 5.25"H x 1"E
 Ctr/Top: 2.75" Ctr/Btm: 6.75"
 3 – 100 Watt E26 Medium
 Acid Washed Glass
 Finishes: BB, CH, MN
 Damp Rated

▼ **1084CH-132**
Chrome
 23.50"W x 9.50"H x 6"E
 Backplate: 7"W x 5.25"H x 1"E
 Ctr/Top: 2.75" Ctr/Btm: 6.75"
 4 – 100 Watt E26 Medium
 Acid Washed Glass
 Finishes: BB, CH, MN
 Damp Rated



▼ **1084MN-132**
Matte Nickel
 23.50"W x 9.50"H x 6"E
 Backplate: 7"W x 5.25"H x 1"E
 Ctr/Top: 2.75" Ctr/Btm: 6.75"
 4 – 100 Watt E26 Medium
 Acid Washed Glass
 Finishes: BB, CH, MN
 Damp Rated



▲ **1083MN-132**
Matte Nickel
 16.75"W x 9.50"H x 6"E
 Backplate: 7"W x 5.25"H x 1"E
 Ctr/Top: 2.75" Ctr/Btm: 6.75"
 3 – 100 Watt E26 Medium
 Acid Washed Glass
 Finishes: BB, CH, MN
 Damp Rated

▲ **1082MN-132**
Matte Nickel
 12"W x 9.50"H x 6"E
 Backplate: 7"W x 5.25"H x 1"E
 Ctr/Top: 2.75" Ctr/Btm: 6.75"
 2 – 100 Watt E26 Medium
 Acid Washed Glass
 Finishes: BB, CH, MN
 Damp Rated



▲ **1082BB-132**
Burnished Bronze
 12"W x 9.50"H x 6"E
 Backplate: 7"W x 5.25"H x 1"E
 Ctr/Top: 6.75" Ctr/Btm: 2.75"
 2 – 100 Watt E26 Medium
 Acid Washed Glass
 Finishes: BB, CH, MN
 Damp Rated



▲ **1083BB-132**
Burnished Bronze
 16.75"W x 9.50"H x 6"E
 Backplate: 7"W x 5.25"H x 1"E
 Ctr/Top: 2.75" Ctr/Btm: 6.75"
 3 – 100 Watt E26 Medium
 Acid Washed Glass
 Finishes: BB, CH, MN
 Damp Rated

▼ **1084BB-132**
Burnished Bronze
 23.50"W x 9.50"H x 6"E
 Backplate: 7"W x 5.25"H x 1"E
 Ctr/Top: 2.75" Ctr/Btm: 6.75"
 4 – 100 Watt E26 Medium
 Acid Washed Glass
 Finishes: BB, CH, MN
 Damp Rated





▲ **1032BB-118**

Burnished Bronze

14"W x 8"H x 8"E

Backplate: 14"W x 4.75"H x 1"E

Ctr/Top: 5.50" Ctr/Btm: 2.50"

2 – 100 Watt E26 Medium

White Faux Alabaster Glass

Finishes: BB, MN

Damp Rated

▶ **1034BB-118**

Burnished Bronze

30"W x 8"H x 8"E

Backplate: 30"W x 4.75"H x 1"E

Ctr/Top: 5.50" Ctr/Btm: 2.50"

4 – 100 Watt E26 Medium

White Faux Alabaster Glass

Finishes: BB, MN

Damp Rated



▶ **1033BB-118**

Burnished Bronze

24"W x 8"H x 8"E

Backplate: 24"W x 4.75"H x 1"E

Ctr/Top: 5.50" Ctr/Btm: 2.50"

3 – 100 Watt E26 Medium

White Faux Alabaster Glass

Finishes: BB, MN

Damp Rated



◀ **1035BB-118**

Burnished Bronze

36"W x 8"H x 8"E

Backplate: 36"W x 4.75"H x 1"E

Ctr/Top: 5.50" Ctr/Btm: 2.50"

5 – 100 Watt E26 Medium

White Faux Alabaster Glass

Finishes: BB, MN

Damp Rated



◀ **1163MN-118**

Matte Nickel

24"W x 8"H x 8"E

Backplate: 24"W x 4.75"H x 1"E

Ctr/Top: 5.50" Ctr/Btm: 2.50"

3 – 100 Watt E26 Medium

White Faux Alabaster Glass

Finishes: BB, MN

Damp Rated



◀ **1164MN-118**

Matte Nickel

30"W x 8"H x 8"E

Backplate:

30"W x 4.75"H x 1"E

Ctr/Top: 5.50" Ctr/Btm: 2.50"

4 – 100 Watt E26 Medium

White Faux Alabaster Glass

Finishes: BB, MN

Damp Rated

▲ **1162MN-118**

Matte Nickel

14"W x 8"H x 8"E

Backplate:

14"W x 4.75"H x 1"E

Ctr/Top: 5.50" Ctr/Btm: 2.50"

2 – 100 Watt E26 Medium

White Faux Alabaster Glass

Finishes: BB, MN

Damp Rated

▶ **1165MN-118**

Matte Nickel

36"W x 8"H x 8"E

Backplate: 36"W x 4.75"H x 1"E

Ctr/Top: 5.50" Ctr/Btm: 2.50"

5 – 100 Watt E26 Medium

White Faux Alabaster Glass

Finishes: BB, MN

Damp Rated





▲ **1362BB-117**
Burnished Bronze
 12"W x 7.25"H x 7.50"E
 Backplate:
 5"W x 5"H x 1.50"E
 Ctr/Top: 3" Ctr/Btm: 4.25"
 2 – 100 Watt E26 Medium
 White Faux Alabaster Glass
 Finishes: BB, CH, MN
 Damp Rated



▲ **1363BB-117**
Burnished Bronze
 19"W x 7.25"H x 8.50"E
 Backplate:
 5"W x 5"H x 1.50"E
 Ctr/Top: 3" Ctr/Btm: 4.25"
 3 – 100 Watt E26 Medium
 White Faux Alabaster Glass
 Finishes: BB, CH, MN
 Damp Rated



▲ **1362CH-117**
Chrome
 12"W x 7.25"H x 7.50"E
 Backplate:
 5"W x 5"H x 1.50"E
 Ctr/Top: 3" Ctr/Btm: 4.25"
 2 – 100 Watt E26 Medium
 White Faux Alabaster Glass
 Finishes: BB, CH, MN
 Damp Rated



▲ **1363CH-117**
Chrome
 19"W x 7.25"H x 8.50"E
 Backplate:
 5"W x 5"H x 1.50"E
 Ctr/Top: 3" Ctr/Btm: 4.25"
 3 – 100 Watt E26 Medium
 White Faux Alabaster Glass
 Finishes: BB, CH, MN
 Damp Rated



▲ **1362MN-117**
Matte Nickel
 12"W x 7.25"H x 7.50"E
 Backplate:
 5"W x 5"H x 1.50"E
 Ctr/Top: 3" Ctr/Btm: 4.25"
 2 – 100 Watt E26 Medium
 White Faux Alabaster Glass
 Finishes: BB, CH, MN
 Damp Rated



▲ **1363MN-117**
Matte Nickel
 19"W x 7.25"H x 8.50"E
 Backplate:
 5"W x 5"H x 1.50"E
 Ctr/Top: 3" Ctr/Btm: 4.25"
 3 – 100 Watt E26 Medium
 White Faux Alabaster Glass
 Finishes: BB, CH, MN
 Damp Rated



▲ **1362BB-297**
Burnished Bronze
 12"W x 7.25"H x 7.50"E
 Backplate:
 5"W x 5"H x 1.50"E
 Ctr/Top: 3" Ctr/Btm: 4.25"
 2 – 100 Watt E26 Medium
 Mist Scavo Glass
 Finish: BB
 Damp Rated



▲ **1363BB-297**
Burnished Bronze
 19"W x 7.25"H x 8.50"E
 Backplate:
 5"W x 5"H x 1.50"E
 Ctr/Top: 3" Ctr/Btm: 4.25"
 3 – 100 Watt E26 Medium
 Mist Scavo Glass
 Finish: BB
 Damp Rated