

Supplement
1606



Contemporary Lighting™



Contemporary Lighting™

COLLECTIONS

Alumilux LED | 187
 Apex | 127
 Apollo | 57
 Argent | 13
 Astro | 109
 Aura | 1
 Billow | 65
 Blade | 125
 Blocs LED | 173
 Bubbly | 107
 Candela | 97
 Caps | 181
 Cells | 73
 Chaos | 17
 Cilandro LED | 182
 Cirque | 121
 Concentric | 49
 Cyclone | 61
 Dazed | 25

Donuts | 101
 Fizz III | 134, 177
 Gem | 179
 Gyro | 45
 Hilite | 139
 Hoops | 115
 Inca | 185
 Jibe | 165
 Kriss Kross | 85
 Light Saber | 5
 Metallika | 41
 Midnight Shower | 21
 Orion | 89
 Palette | 157
 Parasol | 161
 Pizzazz | 169
 Polka | 147
 Puffs | 151
 Quad | 53

Quantum | 111
 Rhombus | 71
 Roller | 69
 Rondelle | 181
 Satellite | 11
 Saturn | 59
 Scepter | 129
 Sense II | 103
 Serpent | 77
 Solitaire | 143
 Spoke | 83
 Squared | 35
 Stage | 183
 Timbale | 79
 Traverse | 43
 Triad | 51
 Turbo | 29
 Volt | 93
 Wake | 33

MORE

Finishes | 194
 Glass | 195
 Index | 191

Lamping Guide | 197
 Replacement Bulbs | 196
 Shades | 194

Warranty | 199

LEGEND



ADA Compliant



Driver Power Source



Installs Up or Down



Adjustable



Low-Voltage Electronic Dimmer



120° Slope



Ballast Power Source



Energy Efficient



Transformer Power Source



LED Dimmer



LED



LED LED



California Title 24



FOR WET LOCATION For Wet Location



DAMP For Damp Location



Dimmable using standard dimmer. Lutron® CL dimmers are recommended.

HCO | Height from Center of Outlet
 OAH | Overall Height




AURA

A sculpture of Polished Chrome channel is gracefully formed with offsetting waves of motion. This collection is fully dimmable for a great combination of form and function.

AURA

- Functional sculptures of illumination
- Fully dimmable high-powered LEDs
- Diodes visible to create contemporary look
- 3000K Color Temperature
- CRI 80+




E21178-PC
LED PCB Pendant
Finish: Polished Chrome
149W LED PCB (Integrated)
10,433 Lumens
38" / 158" OAH



AURA

- Functional sculptures of illumination
- Fully dimmable high-powered LEDs
- Diodes visible to create contemporary look
- 3000K Color Temperature
- CRI 80+



E21176-PC
LED PCB Pendant
Finish: Polished Chrome
103.7W LED PCB (Integrated)
7,258 Lumens
28" / 148" OAH



AURA




E21172-PC



E21172-PC
LED PCB Pendant
Finish: Polished Chrome
32.4W LED PCB (Integrated)
2,268 Lumens
14" / 134" OAH



E21174-PC



E21174-PC
LED PCB Pendant
Finish: Polished Chrome
60.5W LED PCB (Integrated)
4,234 Lumens
22" / 142" OAH







LIGHT SABER

This galactic collection features inter-connected castings finished in Gunmetal, that turn to adjust. Rods of clear acrylic have laser cut lines on the interior which are illuminated by high power LED's enclosed in the castings. Several large scale pieces in the collection designed to fill open spaces in both residential and commercial environments.

- Adjustable arms create individually unique forms
- Large scale pieces finished in gunmetal
- Laser cut pattern within aluminum diffusers to illuminate enclosed LED modules
- 3000K Color Temperature, CRI 80+, dimmable

LIGHT SABER



E41438-75GM


20-Light LED Pendant
 Finish: Gunmetal
 Glass: Clear Acrylic
 60W LED (Integrated)
 4,200 Lumens
 56.5" / 101" OAH

- Includes Two 6" stems ESTR07506GM-SG
- Includes Three 12" stems ESTR07512GM-SG



LIGHT SABER

- Adjustable arms create individually unique forms
- Large scale pieces finished in gunmetal
- Laser cut pattern within aluminum diffusers to illuminate enclosed LED modules
- 3000K Color Temperature, CRI 80+, dimmable




E41437-75GM

24-Light LED Pendant
Finish: Gunmetal
Glass: Clear Acrylic
72W LED (Integrated)
5,040 Lumens
17.75" / 62.25" OAH

- Includes Two 6" stems ESTR07506GM-SG
- Includes Three 12" stems ESTR07512GM-SG



LIGHT SABER




E41436-75GM
24-Light LED Pendant
Finish: Gunmetal
Glass: Clear Acrylic
72W LED (Integrated)
5,040 Lumens
39.5" / 74" OAH

- Includes Two 6" stems ESTR07506GM-SG
- Includes Three 12" stems ESTR07512GM-SG




LIGHT SABER



E41435-75GM
 14-Light LED Pendant
 Finish: Gunmetal
 Glass: Clear Acrylic
 42W LED (Integrated)
 2,940 Lumens
 36.75" / 85" OAH

- Includes Two 6" stems ESTR07506GM-SG
- Includes Three 12" stems ESTR07512GM-SG




E41433-75GM
 10-Light LED Pendant
 Finish: Gunmetal
 Glass: Clear Acrylic
 30W LED (Integrated)
 2,100 Lumens
 44.75" / 94.5" OAH

- Includes Two 6" stems ESTR07506GM-SG
- Includes Three 12" stems ESTR07512GM-SG




LIGHT SABER

- Adjustable arms create individually unique forms
- Large scale pieces finished in gunmetal
- Laser cut pattern within aluminum diffusers to illuminate enclosed LED modules
- 3000K Color Temperature, CRI 80+, dimmable



E41432-75GM
 12-Light LED Pendant
 Finish: Gunmetal
 Glass: Clear Acrylic
 36W LED (Integrated)
 2,520 Lumens
 21.5" / 63" OAH

- Includes Two 6" stems ESTR07506GM-SG
- Includes Three 12" stems ESTR07512GM-SG



E41430-75GM
 2-Light LED Wall Mount
 Finish: Gunmetal
 Glass: Clear Acrylic
 6W LED (Integrated)
 420 Lumens
 HCO: 12"





SATELLITE

A celestial metal frame finished in your choice of Polished Chrome or Bronze support round Clear glass balls which are illuminated by integrated LED modules. Frosted cone shaped diffusers are added as a design element and softly diffuse the light.

SATELLITE


- Uniquely shaped metal frame finished in Polished Chrome or Bronze
- Clear glass balls with cone shaped acrylic diffusers softly illuminate integrated LED modules
- 3000K Color Temperature, CRI 80+, dimmable



E24284-24BZ




E24286-24PC



E24284-24BZ, -24PC

12-Light LED Pendant
 Finish: See Image
 Glass: Clear
 28.8W LED (Integrated)
 2,016 Lumens
 24.5" / 54" OAH

- Includes One 6" stem ESTR06006BZ-AN, PC-AN
- Includes Three 12" stems ESTR06012BZ-AN, PC-AN



E24286-24BZ, -24PC

16-Light LED Pendant
 Finish: See Image
 Glass: Clear
 38.4W LED (Integrated)
 2,688 Lumens
 27.25" / 57" OAH

- Includes One 6" stem ESTR06006BZ-AN, PC-AN
- Includes Three 12" stems ESTR06012BZ-AN, PC-AN





ARGENT


Cages of artfully bend Polished Chrome channel create interesting light forms that are as creative as they are functional. Illuminated from within, high power LED strips gently cast light into the room without glare.

ARGENT

- Shapes of artfully bent Polished Chrome
- Dimmable, High powered LEDs included
- 3000K Color Temperature
- CRI 80+



E24516-PC
LED Pendant
Finish: Polished Chrome
136.08W LED PCB (Integrated)
9,525 Lumens
22" / 142" OAH



ARGENT

- Shapes of artfully bent Polished Chrome
- Dimmable, High powered LEDs included
- 3000K Color Temperature
- CRI 80+



E24514-PC



E24512-PC

E24514-PC
 LED Pendant
 Finish: Polished Chrome
 103.68W LED PCB (Integrated)
 7,258 Lumens
 17.75" / 137.75" OAH

E24512-PC
 LED Pendant
 Finish: Polished Chrome
 69.12W LED PCB (Integrated)
 4,838 Lumens
 14.5" / 134.5" OAH

ARGENT


E24522-PC




E24524-PC




E24526-PC



E24522-PC
 LED Pendant
 Finish: Polished Chrome
 80.64W LED PCB (Integrated)
 5,645 Lumens
 17.75" / 137.75" OAH



E24524-PC
 LED Pendant
 Finish: Polished Chrome
 116.64W LED PCB (Integrated)
 8,165 Lumens
 21" / 141" OAH



E24526-PC
 LED Pendant
 Finish: Polished Chrome
 149.04W LED PCB (Integrated)
 10,433 Lumens
 27" / 147" OAH






CHAOS

This contemporary collection features a cork screw configuration of Polished Chrome metal surrounding bands of 3000K LED. This eclectic approach to lighting design is sure to please those looking for a unique source of light.

- Unique functional sculptures of illumination
- Corkscrew bands with inset high-powered LEDs
- Diodes visible to create contemporary look
- 3000K Color Temperature
- CRI 80+


CHAOS



E21417-PC
 LED Pendant
 Finish: Polished Chrome
 129.6W LED PCB (Integrated)
 9,072 Lumens
 17" / 137" OAH



CHAOS




E21415-PC
LED Pendant
Finish: Polished Chrome
84.2W LED PCB (Integrated)
5,897 Lumens
17" / 137" OAH



- Unique functional sculptures of illumination
- Corkscrew bands with inset high-powered LEDs
- Diodes visible to create contemporary look
- 3000K Color Temperature
- CRI 80+

CHAOS



E21410-PC
 LED Flush Mount
 Finish: Polished Chrome
 90.7W LED PCB (Integrated)
 6,350 Lumens






MIDNIGHT SHOWER

Like the sparkle of the night sky at midnight, elegant strands of smoky crystal bring in the new day as they are suspended by Polished Chrome supports in a linear array. LED modules within the metal frame are diffused to remove glare and allow the crystal to twinkle.

MIDNIGHT SHOWER

- Concealed LED light source
- Smoky crystal strands
- 3000k Color Temperature, CRI 80+, dimmable





E23098-138PC
LED Pendant
Finish: Polished Chrome
Glass: Smoky
40W LED (Integrated)
2,800 Lumens
12" / 123" OAH



MIDNIGHT SHOWER


- Concealed LED light source
- Smoky crystal strands
- 3000k Color Temperature, CRI 80+, dimmable




E23096-138PC
LED Pendant
Finish: Polished Chrome
Glass: Smoky
24W LED (Integrated)
1,680 Lumens
12" / 123" OAH



MIDNIGHT SHOWER



E23094-138PC
 LED Pendant
 Finish: Polished Chrome
 Glass: Smoky
 20W LED (Integrated)
 1,400 Lumens
 18" / 123" OAH



E23091-138PC
 LED Wall Mount
 Finish: Polished Chrome
 Glass: Smoky
 10W LED (Integrated)
 700 Lumens
 HCO: 2.25"





DAZED


Sculptures created from Polished Chrome aluminum rods are formed by hand into a mod-silhouette, perfect for loft living and cosmopolitan lifestyles. Woven through the interior are strings of clear G4 Xenon lamps that add sparkle as they reflect off of the embellished etched patterns of the aluminum. Fashion forward and style genre-defying, the Dazed collection goes with a myriad of looks from art deco to pop art.

DAZED


- Clear string of G4, Xenon Lamps
- State-of-the-art Smith & Kole 12V transformers
- High Polished Chrome Aluminum rods
- Hand formed Mod-Silhouettes
- Dimmable



E22576-PC
15-Light Pendant
Finish: Polished Chrome
15 x 20W G4 (Lamps Included)
3,900 Lumens
36" / 154.75" OAH



DAZED




E22578-PC
12-Light Pendant
Finish: Polished Chrome
12 x 20W G4 (Lamps Included)
3,120 Lumens
24.5" / 133.75" OAH



• Strings of clear G4 Xenon lamps woven through the Interior

DAZED


- Clear string of G4, Xenon Lamps
- State-of-the-art Smith & Kole 12V transformers
- High Polished Chrome Aluminum rods
- Hand formed Mod-Silhouettes
- Dimmable




E22574-PC



E22572-PC



E22574-PC
 12-Light Pendant
 Finish: Polished Chrome
 12 x 20W G4 (Lamps Included)
 3,120 Lumens
 28.5" / 147" OAH



E22572-PC
 8-Light Pendant
 Finish: Polished Chrome
 8 x 20W G4 (Lamps Included)
 2,080 Lumens
 24" / 142" OAH



TURBO


Fins of high quality acrylic are bound together with Polished Chrome trim and illuminated from the top with high power LED. The light from the LED optically travels through the acrylic and mysteriously illuminates the frame as well as the surface below.

- Fins of High Quality acrylic
- Trimmed with Polished Chrome
- Dimmable high power LED lamps included
- 3000K Color Temperature
- CRI 80+

TURBO




E24568-75PC
 LED Pendant
 Finish: Polished Chrome
 Glass: Clear Acrylic
 20W LED PCB (Integrated)
 1,400 Lumens
 25.25" / 144" OAH



TURBO


- Fins of High Quality acrylic
- Trimmed with Polished Chrome
- Dimmable high power LED lamps included
- 3000K Color Temperature
- CRI 80+




E24566-75PC
LED Pendant
Finish: Polished Chrome
Glass: Clear Acrylic
15W LED PCB (Integrated)
1,050 Lumens
19.75" / 138.5" OAH



TURBO



E24562-75PC
LED Pendant
Finish: Polished Chrome
Glass: Clear Acrylic
8W LED PCB (Integrated)
560 Lumens
10" / 128.75" OAH



E24564-75PC
LED Pendant
Finish: Polished Chrome
Glass: Clear Acrylic
10W LED PCB (Integrated)
700 Lumens
13.75" / 132.75" OAH





WAKE

Alternating waves of Polished Chrome mirror each other and create a graceful and soothing look. Strips of LEDs evenly illuminate the space below and are fully dimmable.

- Waves of Polished Chrome mirror
- Strips of LEDs evenly illuminate
- Fully Dimmable
- 3000K Color Temperature
- CRI 80


WAKE




E24541-PC



E24546-PC



E24541-PC
LED Flush Mount
Finish: Polished Chrome
43.2W LED PCB (Integrated)
3,024 Lumens



E24546-PC
LED Pendant
Finish: Polished Chrome
37.8W LED PCB (Integrated)
2,646 Lumens
6.5" / 126.5" OAH



SQUARED


Polished Chrome squares of various sizes mingle to form geometric sculptures of light. With a combination of direct and indirect LED light, this collection is not only an interesting art form but also a unique lighting effect.

- Both direct and Indirect LED Lighting
- Various squares of Polished Chrome metal sculptures
- Dimmable Integrated LEDs
- 3000K Color Temperature
- CRI 80+

SQUARED




E24554-PC
 LED Pendant
 Finish: Polished Chrome
 50.4W LED PCB (Integrated)
 3,528 Lumens
 25.25" / 145.25" OAH



SQUARED


- Both direct and Indirect LED Lighting
- Various squares of Polished Chrome metal sculptures
- Dimmable Integrated LEDs
- 3000K Color Temperature
- CRI 80+




E24555-PC
LED Pendant
Finish: Polished Chrome
77.4W LED PCB (Integrated)
5,418 Lumens
28.25" / 148.25" OAH



SQUARED




E24553-PC
LED Pendant
Finish: Polished Chrome
29.16W LED PCB (Integrated)
2,041 Lumens
20.5" / 140.5" OAH



E24552-PC
LED Pendant
Finish: Polished Chrome
15.12W LED PCB (Integrated)
1,058 Lumens
16" / 136" OAH



SQUARED



E24557-PC
LED Pendant
Finish: Polished Chrome
46.44W LED PCB (Integrated)
3,251 Lumens
36.25" / 156.25" OAH



SQUARED


- Both direct and Indirect LED Lighting
- Various squares of Polished Chrome metal sculptures
- Dimmable Integrated LEDs
- 3000K Color Temperature
- CRI 80+




E24551-PC



E24550-PC




E24551-PC
LED Flush Mount
Finish: Polished Chrome
23.76W LED PCB (Integrated)
1,663 Lumens



E24550-PC
LED Wall Mount
Finish: Polished Chrome
7.2W LED PCB (Integrated)
504 Lumens
HCO: 6.75"

• Can be installed up and down





E24296-AL, -COF, -SC
LED Pendant
Finish: See Images
64.8W LED (Integrated)
4,536 Lumens
6.5" / 126.5" OAH



METALLIKA


Suspended squares of aluminum finished in three beautiful metallic finishes, Brushed Copper, Coffee, or Brushed Aluminum. Driven by high powered integrated LED modules, these classic shapes fit perfectly into today's interiors.

METALLIKA


- Extruded aluminum frame
- Available in three metallic finishes: Brushed Copper, Coffee, and Brushed Aluminum
- 3000K Color Temperature, CRI 80+, dimmable




E24295-AL



E24297-COF



E24295-AL, -COF, -SC
LED Pendant
Finish: See Images
43.2W LED (Integrated)
3,024 Lumens
6.5" / 126.5" OAH



E24297-AL, -COF, -SC
LED Pendant
Finish: See Images
86.4W LED (Integrated)
6,048 Lumens
6.5" / 126.5" OAH





TRAVERSE

Multiple squares finished in Champagne, are layered in a geometric pattern to form an interesting lighting sculpture. Enclosed behind the white acrylic lens is high power LED for even and economical illumination.

TRAVERSE


- All are integrated LED
- Dimmable
- 3000K Color Temperature
- CRI 80




E21515-CHP
LED Pendant
Finish: Champagne
86W LED (Integrated)
6,020 Lumens
7.75" / 127.75" OAH
[Icons: LED, Dimmable]




E21510-CHP



E21510-CHP
LED Wall Mount
Finish: Champagne
28W LED (Integrated)
1,960 Lumens
HCO: 16.75"
[Icons: LED, Dimmable, ADA]



E21513-CHP



E21513-CHP
LED Flush Mount
Finish: Champagne
86W LED (Integrated)
6,020 Lumens
[Icons: LED, Dimmable]

GYRO

Concentric bands of Matte White rotate on 2 axis points to adjust in multiple directions similar to a gyroscope. The edge of each slender band is encased with a small LED strip covered by a frosted lens. It is more a work of art than just a lighting fixture.

- Rotatable bands finished in Matte White
- Strip of LED encased in frosted lens along edge
- 3000K Color Temperature, CRI 80+, dimmable


GYRO



E24586-MW
 LED Pendant
 Finish: Matte White
 119.52W LED (Integrated)
 8,366 Lumens
 33" / 153" OAH


GYRO

- Rotatable bands finished in Matte White
- Strip of LED encased in frosted lens along edge
- 3000K Color Temperature, CRI 80+, dimmable




E24584-MW

LED Pendant
Finish: Matte White
92.52W LED (Integrated)
6,476 Lumens
27" / 147" OAH






E24580-MW




E24582-MW

E24580-MW
 LED Flush Mount
 Finish: Matte White
 52.2W LED (Integrated)
 3,654 Lumens




E24582-MW
 LED Pendant
 Finish: Matte White
 52.2W LED (Integrated)
 3,654 Lumens
 21" / 141" OAH



CONCENTRIC

Four Bronze concentric rings strategically placed in orbit to form a spherical lighting design as unique as it is functional. With the internal placement of LED strips the light moves both direct and indirect depending on where you are in relation to the fixture.



E24049-BZ
LED Pendant
Finish: Bronze
100W LED PCB (Integrated)
7,000 Lumens
48.25" / 85.25" OAH

- Includes One 6" extension stem ESTR06206BZ-JM
- Includes Two 12" extension stems ESTR06212BZ-JM
- Includes One 12" extension stem w/"U" Joint ESTR06212BZS-JM




CONCENTRIC

- Adjustable aluminum rings house high-powered integrated PCB LEDs
- Spherical lighting design with acrylic diffuser
- 3000K Color Temperature
- CRI>80



E24048-BZ



E24048-BZ
LED Pendant
Finish: Bronze
80W LED PCB (Integrated)
3,675 Lumens
39.25" / 75.25" OAH

- Includes One 6" extension stem ESTR06206BZ-JM
- Includes Two 12" extension stems ESTR06212BZ-JM
- Includes One 12" extension stem w/"U" Joint ESTR06212BZS-JM



TRIAD

Triangular shape Matte White tubing intersect to form a creative and artful approach to lighting. Dimmable LED adds softness and control for the ultimate in comfortable living.

TRIAD

- Matte White tubing intersect to form creative shadow casting
- Dimmable LED
- 3000K Color Temperature
- CRI 80



E23073-MW



E23077-MW

E23073-MW
 LED Flush Mount
 Finish: Matte White
 24W LED PCB (Integrated)
 1,680 Lumens

23.75"
 22.25"

E23077-MW
 LED Flush Mount
 Finish: Matte White
 50W LED PCB (Integrated)
 3,500 Lumens

37"
 32.25"




QUAD

Cubist art reimagined through lighting, the Quad collection features suspended aluminum squares finished in a warm Bronze in multiple tiers, illuminated by high powered dimmable LEDs housed within the frame. The collection offers tremendous design flexibility with adjustable connectors for multiple configurations. The hanging illuminated squares serve as kinetic sculptures, adding a dimension of movement of the room.

QUAD



- Adjustable connectors allowing for various combinations
- Extruded Aluminum
- 3000K Color temperature
- Dimmable LEDs




E22407-BZ
3-Tier LED Pendant
Finish: Bronze
Glass: Acrylic
100W LED (Integrated)
7,000 Lumens
20.5" / 47.25" OAH



• Can be arranged in different sequences



QUAD




E22405-BZ
2-Tier LED Pendant
Finish: Bronze
Glass: Acrylic
55W LED (Integrated)
3,850 Lumens
11.75" / 47.25" OAH



QUAD

- Adjustable connectors allowing for various combinations
- Extruded Aluminum
- 3000K Color temperature
- Dimmable LEDs



E22408-BZ
LED Flush Mount
Finish: Bronze
Glass: Acrylic
100W LED (Integrated)
6,500 Lumens



• Lights on



• Lights off




• Adjusted 3-tier

APOLLO


These Matte White circular pendants have the LED board concealed up inside the ring where it is invisible. The light bounces off an internal aluminum reflector and down onto the surface below. The result is a soft illumination without an ounce of glare.

E20226-MW
LED Pendant
Finish: Matte White
33W LED (Integrated)
2,310 Lumens
8" / 128" OAH



- Hidden high-powered LED source inside ring
- Internal Aluminum Reflector to direct light
- 3000K Color Temperature
- CRI 80

APOLLO



E20225-MW
 LED Pendant
 Finish: Matte White
 21W LED (Integrated)
 1,470 Lumens
 8" / 128" OAH





SATURN

The Saturn truly lives up to its name with rings of Metallic Silver or Bronze cast metal supporting bands of Frost acrylic. The LED lights add an out of this world touch with illumination that can be controlled with a standard wall dimmer.

SATURN



- Two finish options available, Metallic Silver or Bronze
- Lutron® CL™ Dimmers are recommended
- Adjusts to Multiple configuration
- 3000K Color Temperature




E22455-11BZ




E22456-11MS




E22453-11MS



E22456-11BZ, -11MS
 3-Tier LED Pendant
 Finish: See Images
 Glass: Frost Acrylic
 70W LED (Integrated)
 4,900 Lumens
 35.75" / 109" OAH



E22455-11BZ, -11MS
 2-Tier LED Pendant
 Finish: See Images
 Glass: Frost Acrylic
 40W LED (Integrated)
 2,800 Lumens
 35.75" / 51.5" OAH



E22453-11BZ, -11MS
 1-Tier LED Pendant
 Finish: See Images
 Glass: Frost Acrylic
 24W LED (Integrated)
 1,680 Lumens
 35.75" / 51.5" OAH






CYCLONE

Twisted aluminum channels of Matte White terminate into solid castings to form unique and functional lighting designs. Large scale pieces can be used in conference rooms and tall entries with the comfort of long life LED on board.

- Twisted aluminum channels terminate at solid castings
- Unique and functional LED lighting designs
- Large scale pieces for commercial and residential applications
- 3000K Color Temperature, CRI 80+, dimmable

CYCLONE




E41396-11MW
 LED Pendant
 Finish: Matte White
 44W LED (Integrated)
 3,080 Lumens
 10.75" / 129.75" OAH




CYCLONE



E41390-11MW



E41398-11MW
LED Floor Lamp
Finish: Matte White
44W LED (Integrated)
3,080 Lumens



E41390-11MW
LED Pendant
Finish: Matte White
23W LED (Integrated)
1,610 Lumens
10.5" / 128.75" OAH




CYCLONE

- Twisted aluminum channels terminate at solid castings
- Unique and functional LED lighting designs
- Large scale pieces for commercial and residential applications
- 3000K Color Temperature, CRI 80+, dimmable




E41394-11MW
LED Pendant
Finish: Matte White
44W LED (Integrated)
3,080 Lumens
78.5" / 198.5" OAH



E41392-11MW
LED Pendant
Finish: Matte White
23W LED (Integrated)
1,610 Lumens
49.75" / 169.75" OAH







BILLOW

Cast metal frames of Matte White waves come together to create an interesting design that is as pleasant to look at as it is a very functional light source. High power LED move ample light into the room but can be dimmed to your desired intensity.

- Cast metal frames of Matte White waves
- Dimmable High powered LEDs included
- 3000K Color Temperature
- CRI 80

BILLOW




E24127-MW
 LED PCB Pendant
 Finish: Matte White
 90W LED PCB (Integrated)
 6,300 Lumens
 39.5" / 126" OAH




BILLOW

- Cast metal frames of Matte White waves
- Dimmable High powered LEDs included
- 3000K Color Temperature
- CRI 80




E24125-MW
LED PCB Pendant
Finish: Matte White
24W LED PCB (Integrated)
1,680 Lumens
39.5" / 126" OAH







• Wall Mount Option



E24120-MW
 LED PCB Flush/Wall Mount
 Finish: Matte White
 36W LED PCB (Integrated)
 2,520 Lumens




• Wall Mount Option



E24122-MW
 LED PCB Flush/Wall Mount
 Finish: Matte White
 47W LED PCB (Integrated)
 3,290 Lumens



• Wall Mount Option





E24124-MW
 LED PCB Flush/Wall Mount
 Finish: Matte White
 55W LED PCB (Integrated)
 3,850 Lumens



ROLLER

Dual pieces of Matte White aluminum gently wave in tandem to create a unique contemporary form. With powerful COB LEDs mounted on top and bottom, you receive ample down light and an indirect up light that creates a dramatic effect in the room.




E22824-MW
LED Pendant
Finish: Matte White
35W COB LED (Integrated)
2,450 Lumens
4.75" / 121" OAH



ROLLER


- Gentle waves of aluminum in Matte White finish
- High-powered integrated LED modules
- 3000K Color Temperature
- Designed to give ample down light and ambient up light




E22822-MW

E22820-MW

• Uplight



• Downlight



E22822-MW
 LED Pendant
 Finish: Matte White
 25W COB LED (Integrated)
 1,750 Lumens
 4.75" / 121" OAH


4.75" □
 1" □
 37"

4.75" □
 29.5"
 7.25"


E22820-MW
 LED Wall Mount
 Finish: Matte White
 20W COB LED (Integrated)
 1,400 Lumens
 HCO: 7.25"

RHOMBUS

Large scale rectangular forms suspend gracefully in mid-air to fill a large space without a bulky appearance. LEDs are cleverly concealed in both the bottom and the top to provide a combination of up and down light. Available in your choice of Matte White or Bronze.



BZ Bronze




E22866-BZ, -MW
LED Pendant
Finish: See Images
51W LED (Lamps Included)
3,570 Lumens
20.25" / 137.75" OAH




RHOMBUS

- Concealed LED in bottom of thin-profile rectangular forms
- Available in Matte White and Bronze finish
- 3000K Color Temperature
- CRI 80



MW Matte White




E22864-BZ, -MW
LED Pendant
Finish: See Images
43W LED (Lamps Included)
3,010 Lumens
17" / 134.5" OAH



• Uplight



• Downlight



E20175-11MS
3-Light Pendant
Finish: Metallic Silver
Glass: Matte White
64.2W LED (Lamps Included)
4,494 Lumens
10" / 130" OAH




CELLS

Intersecting circles form a collage of LED luminaires that become the focal point of the room. The collection features two pendants, as well as three sizes of modular ceiling fixtures in Metallic Silver which can link together to form an artful array of light.

CELLS



- Customizable, modular ceiling fixtures are easily linked together
- Acrylic diffuser to soften light output
- Up to 10 Mods controlled by one J box
- Dimmable LED
- 3000K Color Temperature
- CRI 80




E20177-11MS
5-Light Pendant
Finish: Metallic Silver
Glass: Matte White
97.8W LED (Lamps Included)
6,846 Lumens
10" / 130" OAH




CELLS


The Cells collection is a modular system that allows for one unit to install on a powered outlet and up to 10 additional units of your choice to be added to the original module with the additional wire included inside each fixture. The additional wire moves from fixture to fixture through knockouts on the side. This system allows the user to create a sculpture of light on ceiling sure to become the focal point in the room.




E20171-11MS
1-Light Flush Mount
Finish: Metallic Silver
Glass: Matte White
12W LED (Lamps Included)
840 Lumens



E20172-11MS
1-Light Flush Mount
Finish: Metallic Silver
Glass: Matte White
21.6W LED (Lamps Included)
1,512 Lumens



E20173-11MS
1-Light Flush Mount
Finish: Metallic Silver
Glass: Matte White
30.6W LED (Lamps Included)
2,142 Lumens





- Customizable, modular ceiling fixtures are easily linked together
- Acrylic diffuser to soften light output
- Up to 10 Mods controlled by one J box
- Dimmable LED
- 3000K Color Temperature
- CRI 80



1 x E20171-11MS
1 x E20172-11MS
1 x E20173-11MS



2 x E20171-11MS
2 x E20172-11MS
1 x E20173-11MS



2 x E20171-11MS
3 x E20172-11MS
2 x E20173-11MS




SERPENT


Wall lighting or wall décor? This collection satisfies both. A White pre-bent aluminum channel encases a LED strip which casts a unique pattern on the wall. Both functional and decorative, this unique sculpture is sure to be the focal point of the room.

- Flat White pre-bent aluminum channel
- Both functional and decorative LED Strips
- 3000K Color Temperature
- CRI 80+

SERPENT



E24533-WT




E24531-WT



E24532-WT


E24531-WT

LED Wall Mount
 Finish: White
 14.5W LED PCB (Integrated)
 1,015 Lumens
 HCO: 13.25"




E24533-WT

LED Wall Mount
 Finish: White
 18W LED PCB (Integrated)
 1,260 Lumens
 HCO: 12.5"



E24532-WT


LED Wall Mount
 Finish: White
 13W LED PCB (Integrated)
 910 Lumens
 HCO: 9"





TIMBALE

A series of round Die Cast rings, finished in Polished Chrome, are edge lit with high quality LEDs. Many of the rings are adjustable, allowing for unique design arrangements and light to be directed where needed.




E21146-01PC
11-Light Semi Flushmount
Finish: Polished Chrome
Glass: Acrylic
110W LED (Lamps Included)
9,900 Lumens




TIMBALE

- Die Cast finished in Polished Chrome
- Edge lit with High quality LEDs
- Adjustable rings for directional lighting
- 3000K Color Temperature



E21144-01PC
 7-Light Pendant
 Finish: Polished Chrome
 Glass: Acrylic
 56.4W LED (Lamps Included)
 5,076 Lumens
 24" / 42.25" OAH


• Telescopic Stem



E21142-01PC
 1-Light Pendant
 Finish: Polished Chrome
 Glass: Acrylic
 10.8W LED (Lamps Included)
 972 Lumens
 8.5" / 128.5" OAH



• Adjustable Die Cast rings to allow for unique design arrangements, and directional lighting.



TIMBALE



E21148-01PC




E21141-01PC




E21140-01PC



E21141-01PC
 1-Light Flush Mount
 Finish: Polished Chrome
 Glass: Acrylic
 10.8W LED (Lamps Included)
 972 Lumens




E21148-01PC
 11-Light Pendant
 Finish: Polished Chrome
 Glass: Acrylic
 110W LED (Lamps Included)
 9,900 Lumens
 4.25" / 124.25" OAH



E21140-01PC
 1-Light Adjustable Flush Mount/Wall Mount
 Finish: Polished Chrome
 Glass: Acrylic
 6W LED (Lamps Included)
 540 Lumens





SPOKE

Square tube arms protrude from a polygonal cast hub with recessed acrylic lenses at its ends to conceal LED modules for direct and indirect up-down illumination. Available in both 6 and 8 arm configurations and 3 finish options Matte White, Brushed Aluminum, and Coffee.

- Cast and extruded aluminum available in 3 finishes: Matte White, Brushed Aluminum and Coffee
- Hidden LED light source behind recessed frosted acrylic lenses
- Up-Down Light
- 3000K Color Temperature, CRI 80+, dimmable

SPOKE



E21026-MW
MW Matte White



E21028-COF
COF Coffee




AL Aluminum




COF Coffee



MW Matte White




AL Aluminum



E21026-AL, -COF, -MW

LED Pendant
Finish: See Images
36W LED (Integrated)
2,520 Lumens
27.5" / 73.25" OAH

- Includes One 6" stem
ESTR06206AL-JM, COF-JM, MW-JM
- Includes Three 12" stems
ESTR06212AL-JM, COF-JM, MW-JM



E21028-AL, -COF, -MW

LED Pendant
Finish: See Images
51W LED (Integrated)
3,570 Lumens
27.5" / 73.25" OAH

- Includes One 6" stem
ESTR06206AL-JM, COF-JM, MW-JM
- Includes Three 12" stems
ESTR06212AL-JM, COF-JM, MW-JM






KRISS KROSS

Micro channels of Polished Chrome aluminum are faced with an acrylic diffuser and are arranged in a crisscross formation to create an interesting sculpture of light. Although pre-set out of the box, each are adjustable so to create your own unique design.

KRISS KROSS

- Thin strips of LED are housed in channels of Polished Chrome Aluminum
- Arranged in a crisscross formation to create functional sculptures of light
- Adjustable to create your own design
- 3000K Color Temperature
- CRI 80




E20697-PC
16-Light Pendant
Finish: Polished Chrome
91.2W LED (Integrated)
6,384 Lumens
52.25" / 84.5" OAH

- Includes One 6" stem **ESTR06206PC**
- Includes Three 12" stems **ESTR06212PC**



KRISS KROSS



E20695-PC
8-Light Pendant
Finish: Polished Chrome
45.6W LED (Integrated)
3,192 Lumens
31" / 72.75" OAH

- Includes One 6" stem **ESTR06206PC**
- Includes Three 12" stems **ESTR06212PC**



KRISS KROSS


- Thin strips of LED are housed in channels of Polished Chrome Aluminum
- Arranged in a crisscross formation to create functional sculptures of light
- Adjustable to create your own design
- 3000K Color Temperature
- CRI 80




E20693-PC



E20691-PC



E20693-PC
 6-Light Flush Mount
 Finish: Polished Chrome
 34.2W LED (Integrated)
 2,394 Lumens



E20691-PC
 3-Light Wall Mount
 Finish: Polished Chrome
 17.1W LED (Integrated)
 1,197 Lumens
 HCO: 13"





ORION

Spiraling tentacles of Polished Chrome metal create lighting works of art. Long lasting and easily replaceable LED bulbs grace the end of the arms emitting light and sparkle that is sure to add character to any space.

ORION



- Lamps Included
- Energy Efficient
- 3000K Color Temperature
- CRI 80+, dimmable



E24676-PC

49-Light LED Pendant
Finish: Polished Chrome
58.8W LED (Lamps Included)
5,390 Lumens
49" / 94" OAH

- Includes One 6" stem ESTR06206PC-DZ
- Includes Three 12" stems ESTR06212PC-DZ



ORION



- Lamps Included
- Energy Efficient
- 3000K Color Temperature
- CRI 80+, dimmable



E24674-PC

39-Light LED Pendant
Finish: Polished Chrome
46.8W LED (Lamps Included)
4,290 Lumens
39.5" / 85" OAH


- Includes One 6" stem ESTR06206PC-DZ
- Includes Three 12" stems ESTR06212PC-DZ




ORION




E24670-PC



E24672-PC



E24672-PC
 13-Light LED Wall Mount
 Finish: Polished Chrome
 15.6W LED (Lamps Included)
 1,430 Lumens
 HCO: 13.75"




E24670-PC
 20-Light LED Flush Mount
 Finish: Polished Chrome
 24W LED (Lamps Included)
 2,200 Lumens



VOLT

This contemporary design features oval shaped die cast cups finished in Polished Chrome or Bronze which supports matching shape bubble glass shades. Each cup has dual LED modules which both light the glass shade above and provide down light below.




E22898-89BZ, -89PC
16-Light Pendant
Finish: See Images
Glass: Etched/Bubble
16 x 3W LED (Lamps Included)
3,360 Lumens
8" / 120" OAH





- 3000K Color Temperature
- Indirect Up-Light and Direct Down-Light
- Solid oval shape, Etched Bubble Glass shades



Frame diagram and overall measurements


E22897-89BZ, -89PC

16-Light Pendant
 Finish: See Images
 Glass: Etched/Bubble
 16 x 3W LED (Lamps Included)
 3,360 Lumens
 6" / 44.75" OAH

- Includes Two 6" stems ESTR06206BZ, PC
- Includes Six 12" stems ESTR06212BZ, PC



VOLT



Frame diagram and overall measurements

E22899-89BZ, -89PC

16-Light Pendant

Finish: See Images

Glass: Etched/Bubble

16 x 3W LED (Lamps Included)

3,360 Lumens

6" / 44.75" OAH

- Includes Two 6" stems ESTR06206BZ, PC
- Includes Six 12" stems ESTR06212BZ, PC




- 3000K Color Temperature
- Indirect Up-Light and Direct Down-Light
- Etched Bubble Glass shades


VOLT




E22891-89BZ, -89PC
 2-Light Bath Vanity
 Finish: See Images
 Glass: Etched/Bubble
 2 x 3W LED (Lamps Included)
 420 Lumens
 HCO: 2.5"




E22892-89BZ, -89PC
 4-Light Bath Vanity
 Finish: See Images
 Glass: Etched/Bubble
 4 x 3W LED (Lamps Included)
 840 Lumens
 HCO: 1.8"




E22893-89BZ, -89PC
 6-Light Bath Vanity
 Finish: See Images
 Glass: Etched/Bubble
 6 x 3W LED (Lamps Included)
 1,260 Lumens
 HCO: 1.8"



E22894-89BZ, -89PC
 8-Light Bath Vanity
 Finish: See Images
 Glass: Etched/Bubble
 8 x 3W LED (Lamps Included)
 1,680 Lumens
 HCO: 1.8"



E22896-89BZ, -89PC
 12-Light Bath Vanity
 Finish: See Images
 Glass: Etched/Bubble
 12 x 3W LED (Lamps Included)
 2,520 Lumens
 HCO: 1.8"






CANDELA

Cone shaped acrylic diffusers are supported by arms that branch out of a central stem to create a European-modern look in this chandelier, finished in either Bronze or Polished Chrome. These large scale LED chandeliers would be at home in either dining or entry hall applications.

CANDELA

- Modern take on the traditional chandelier
- Cone shaped acrylic diffusers
- Finished in either Bronze or Polished Chrome
- 3000K Color Temperature, CRI 80+, dimmable



E24367-09BZ, -09PC

60-Light LED Pendant

Finish: See Image

Glass: Frost White


72W LED (Integrated)

5,040 Lumens

21.25" / 141.25" OAH



CANDELA





E24365-09BZ, -09PC

36-Light LED Pendant
Finish: See Image
Glass: Frost White
43.2W LED (Integrated)
3,024 Lumens
15.75" / 135.75" OAH



CANDELA

- Modern take on the traditional chandelier
- Cone shaped acrylic diffusers
- Finished in either Bronze or Polished Chrome
- 3000K Color Temperature, CRI 80+, dimmable



E24363-09BZ, -09PC

24-Light LED Pendant
Finish: See Image
Glass: Frost White
57.6W LED (Integrated)
4,032 Lumens
18" / 138" OAH



DONUTS

The Donut collection is a nod to retro, industrial and modern design sensibilities. Each fixture features floating round donuts of spun steel finished in a mirror like Polished Chrome. Clustered together, these rings house LEDs that glow upward into the white interior reflectors that move light indirectly out of the fixture without the glare of a direct light source.



E22599-PC


9-Light Pendant

Finish: Polished Chrome

9 x 16W LED (Lamps Included)

10,080 Lumens

4.75" / 124.25" OAH



LED is thrown upwards into the white interior reflectors of the rings. Those reflectors then move light indirectly out and into the room, without the glare of a direct source.

DONUTS


- Dimmable LED
- 3000K Color Temperature
- High Polished Chrome
- Even distribution of light




E22591-PC



E22596-PC



E22591-PC
 1-Light Pendant
 Finish: Polished Chrome
 1 x 16W LED (Lamp Included)
 1,120 Lumens
 4.75" / 124.25" OAH



E22596-PC
 6-Light Pendant
 Finish: Polished Chrome
 6 x 16W LED (Lamps Included)
 6,720 Lumens
 4.75" / 124.25" OAH






SENSE II

The Sense II collection lends an air of cosmic mysticism with Mirror Chrome plate glass shades that are hand etched for added dimension. The sinuous curves hint at eccentric glamour and feature modern technology with its state-of-the-art Smith & Kole 12-volt transformer, among the best in the market. This sculptural fixture commands the center of attention, anchoring the look of a living space.

SENSE II

- G9, Xenon Lamps Included
- Mirror Chrome Plated
- Hand Etched details
- Teardrop Crystal pendants trim detail



E21406-81PC
6-Light Pendant
Finish: Polished Chrome
Glass: Mirror Chrome
6 x 40W G9 (Lamps Included)
3,000 Lumens
11.5" / 128" OAH

SENSE II


- G9, Xenon Lamps Included
- Mirror Chrome Plated
- Hand Etched details
- Teardrop Crystal pendants trim detail




E21409-81PC



E21405-81PC



E21409-81PC
 1-Light Wall Mount
 Finish: Polished Chrome
 Glass: Mirror Chrome
 1 x 40W G9 (Lamp Included)
 500 Lumens
 HCO: 3.5"



E21405-81PC
 5-Light Pendant
 Finish: Polished Chrome
 Glass: Mirror Chrome
 5 x 40W G9 (Lamps Included)
 2,500 Lumens
 11.25" / 128" OAH





E21399-81PC




E21401-81PC



E21403-81PC


E21399-81PC

3-Light Flush Mount
 Finish: Polished Chrome
 Glass: Mirror Chrome
 3 x 40W G9 (Lamps Included)
 1,500 Lumens




E21403-81PC

6-Light Flush Mount
 Finish: Polished Chrome
 Glass: Mirror Chrome
 6 x 40W G9 (Lamps Included)
 3,000 Lumens



E21401-81PC

5-Light Flush Mount
 Finish: Polished Chrome
 Glass: Mirror Chrome
 5 x 40W G9 (Lamps Included)
 2,500 Lumens





BUBBLY

Effervescent Bubble glass balls are randomly placed on rods of Polished Chrome and illuminated by high power LED diodes enclosed in the base. The rod swivels 180 degrees so that light can be positioned where needed.

BUBBLY


- Bubble glass balls placed randomly on a Polished Chrome rod
- Illuminated by high powered dimmable LEDs
- Rod swivels a full 180 degrees
- 3000K Color Temperature
- CRI 80+



E24571-91PC

9-Light LED PCB Pendant
 Finish: Polished Chrome
 Glass: Bubble
 22.5W LED PCB (Lamps Included)
 1,575 Lumens
 12.5" / 50" OAH


- Includes One 6" stem ESTR12506PC-LX
- Includes Three 12" stems ESTR12512PC-LX




E24573-91PC

21-Light LED PCB Pendant
 Finish: Polished Chrome
 Glass: Bubble
 52.5W LED PCB (Lamps Included)
 3,675 Lumens
 36" / 72" OAH

- Includes One 6" stem ESTR12506PC-LX
- Includes Three 12" stems ESTR12512PC-LX






ASTRO

Round Black tubing orbit an elliptical shape satin white glass and support sails of perforated stainless steel to create a unique lighting sculpture. A LED light source sheds soft and economical into the room while adding years of maintenance free illumination.

- Satin white elliptical shape glass
- Round black metal tubing
- Perforated stainless steel sails
- Dimmable, LED lamps included
- 3000K Color Temperature
- CRI 80

ASTRO



E21059-01BKSST

1-Light Pendant
 Finish: Black/Stainless Steel
 Glass: White
 11W LED (Lamps Included)
 161 Lumens
 25" / 72.5" OAH

- Includes Two 6" stems ESTR05006BK-SG
- Includes Three 12" stems ESTR05012BK-SG




QUANTUM

These Black aluminum pendants are unique in that they are formed as a tapered cylinder open at both the top and bottom. LEDs are mounted on the very top projecting down into a white acrylic diffuser, lining the inside of the pendant. The opening at the top provides up-light, as well as down-light.




QUANTUM

- Black Aluminum pendants with tapered cylinder
- Open bottom and top to provide up and down-lighting
- White Acrylic diffuser
- CRI 80+



E20908-BK
 LED Pendant
 Finish: Black
 Glass: Acrylic
 2 x 40W LED (Integrated)
 5,600 Lumens
 13.5" / 133.5" OAH



E20906-BK
 LED Pendant
 Finish: Black
 Glass: Acrylic
 2 x 30W LED (Integrated)
 3,500 Lumens
 10.5" / 130.5" OAH



• View from top



QUANTUM



E20905-BK



E20903-BK



E20902-BK



E20903-BK
 LED Pendant
 Finish: Black
 Glass: Acrylic
 35W LED (Integrated)
 2,450 Lumens
 4.25" / 123" OAH

E20905-BK
 LED Pendant
 Finish: Black
 Glass: Acrylic
 58W LED (Integrated)
 4,060 Lumens
 4" / 122.75" OAH


E20902-BK
 LED Wall Mount
 Finish: Black
 Glass: Acrylic
 7W LED (Integrated)
 490 Lumens
 HCO: 6"

QUANTUM

- Black Aluminum pendants with tapered cylinder
- Open bottom and top to provide up and down-lighting
- White Acrylic diffuser
- CRI 80+



E20904-BK
 LED Pendant
 Finish: Black
 Glass: Acrylic
 41W LED (Integrated)
 2,870 Lumens
 4" / 122.75" OAH



E20901-BK
 LED Pendant
 Finish: Black
 Glass: Acrylic
 7W LED (Integrated)
 490 Lumens
 4.25" / 123" OAH






HOOPS

Multiple sizes of Polished Chrome hoops of light can be playfully arranged in various configurations for a power presentation. Continuous strips of LEDs are mounted inward towards the center of the hoop for an indirect display of light.



- Polished Chrome “hoops” adjustable to your preference
- LEDs mounted inward to provide indirect light
- 3000K Color Temperature
- CRI 80+

HOOPS




E22716-PC
 11-Light Pendant
 Finish: Polished Chrome
 Glass: Acrylic
 65.2W LED PCB (Integrated)
 4,561 Lumens
 23" / 143" OAH



HOOPS



• Multiple arrangement options



E22715-PC
3-Tier Pendant
Finish: Polished Chrome
Glass: Acrylic
30.6W LED PCB (Integrated)
2,142 Lumens
12" / 130" OAH




HOOPS



- Polished Chrome “hoops” adjustable to your preference
- LEDs mounted inward to provide indirect light
- 3000K Color Temperature
- CRI 80+



- Multiple arrangement options




E22714-PC
2-Tier Pendant
Finish: Polished Chrome
Glass: Acrylic
23W LED PCB (Integrated)
1,680 Lumens
12" / 130" OAH



HOOPS


- Polished Chrome “hoops” adjustable to your preference
- LEDs mounted inward to provide indirect light
- 3000K Color Temperature
- CRI 80+




E22713-PC
1-Tier Pendant
Finish: Polished Chrome
Glass: Acrylic
13.3W LED PCB (Integrated)
932 Lumens
5" / 125" OAH




HOOPS





E22712-PC
 1-Tier Pendant
 Finish: Polished Chrome
 Glass: Acrylic
 8.6W LED PCB (Integrated)
 605 Lumens
 5" / 125" OAH

E22710-PC
 1-Light Wall Mount
 Finish: Polished Chrome
 Glass: Acrylic
 5.4W LED PCB (Integrated)
 378 Lumens
 HCO: 1.58"






CIRQUE


Matte White rings suspend in a unique fashion as if relying on each other for support. A continuous band of LED evenly spread generous amounts of dimmable light into the space. Ceiling fixtures can also double as wall mounts.

CIRQUE

- High-powered LED rings that fit into each other
- Ceiling Mounts also function as Wall Sconces
- 3000K Color Temperature
- CRI 80+



E22849-MW
 LED Pendant
 Finish: Matte White
 Glass: Acrylic
 195W LED (Integrated)
 13,650 Lumens
 20" / 134" OAH




E22847-MW
 LED Pendant
 Finish: Matte White
 Glass: Acrylic
 67W LED (Integrated)
 4,690 Lumens
 13" / 126" OAH




CIRQUE


- High-powered LED rings that fit into each other
- Ceiling Mounts also function as Wall Sconces
- 3000K Color Temperature
- CRI 80+



E22848-MW



E22845-MW
 LED Pendant
 Finish: Matte White
 Glass: Acrylic
 51W LED (Integrated)
 3,570 Lumens
 12" / 121" OAH



E22848-MW
 LED Pendant
 Finish: Matte White
 Glass: Acrylic
 100W LED (Integrated)
 7,000 Lumens
 16" / 129" OAH




CIRQUE



• Wall Mount Option

E22840-MW


LED Flush/Wall Mount
Finish: Matte White
Glass: Acrylic
20W LED (Integrated)
1,400 Lumens



• Wall Mount Option


E22841-MW


LED Flush/Wall Mount
Finish: Matte White
Glass: Acrylic
31W LED (Integrated)
2,170 Lumens



E22843-MW

LED Semi-Flushmount
Finish: Matte White
Glass: Acrylic
43W LED (Integrated)
3,010 Lumens





4.75" [



E22906-BZ
LED Pendant
Finish: Bronze
36W LED (Integrated)
2,520 Lumens
7.5" / 125" OAH



4.75" [



53.75"

BLADE

A thin blade of Bronze aluminum incorporates a micro size LED board recessed into the bottom. The result is a unique effect of light appearing on the surface below without a clear indication from where it is generated.


BLADE

- Low-profile aluminum “blade” with integrated LED board recessed into bottom
- Dark Bronze finish
- 3000K Color Temperature
- CRI 80+



E22902-BZ

• Close up view



E22904-BZ

4.75" [



E22902-BZ
LED Pendant
Finish: Bronze
26W LED (Integrated)
1,820 Lumens
7.5" / 125" OAH



4.75" [



32.5"

4.75" [



E22904-BZ
LED Pendant
Finish: Bronze
35W LED (Integrated)
2,450 Lumens
7.5" / 125" OAH



4.75" [




43.25"



APEX

This Danish modern collection of large scale pendants is on trend. Available in two sizes and two finishes, White and Steel Blue, these pendants are not only functional but also add a splash of color to any space.


- Large scale pendants
- Two color options, Steel Blue or White
- Incandescent




E20639-SB



E20638-WT



E20639-SB, -WT
 1-Light Pendant
 Finish: See Images
 1 x 60W MB Lamp
 672 Lumens
 20" / 138" OAH



E20638-SB, -WT
 1-Light Pendant
 Finish: See Images
 1 x 60W MB Lamp
 672 Lumens
 14.5" / 132" OAH





SCEPTER

Slender beveled cut rods of bubble glass, illuminated by high power LED modules, suspend in an array of fashionable configurations. Available in Black Chrome with Clear bubble glass and Anodized Bronze with Champagne bubble glass.

SCEPTER

- Multi-faceted prisms with inner bubbles available in Clear or Champagne
- Finishes available in Black Chrome and Anodized Bronze
- 3000K Color Temperature



E32778-91BC




• Clear bubble glass



• Champagne bubble glass



E32778-91BC, -118BRZ
 10-Light Pendant
 Finish: See Images
 Glass: See Images
 75W LED (Lamps Included)
 2,460 Lumens
 140" OAH



E32775-91BC, -118BRZ
 5-Light Pendant
 Finish: See Images
 Glass: See Images
 37.5W LED (Lamps Included)
 1,230 Lumens
 140" OAH




SCEPTER



E32779-91BC




E32776-118BRZ



E32779-91BC, -118BRZ

10-Light Pendant
 Finish: See Images
 Glass: See Images
 75W LED (Lamps Included)
 2,460 Lumens
 20"/140" OAH



E32776-91BC, -118BRZ

6-Light Pendant
 Finish: See Images
 Glass: See Images
 45W LED (Lamps Included)
 1,476 Lumens
 20"/140" OAH



SCEPTER

- Multi-faceted prisms with inner bubbles available in Clear or Champagne
- Finishes available in Black Chrome and Anodized Bronze
- 3000K Color Temperature




E32774-91BC




E32771-91BC




E32770-118BRZ



E32774-91BC, -118BRZ
 4-Light Pendant
 Finish: See Images
 Glass: See Images
 30W LED (Lamps Included)
 984 Lumens
 20"/140" OAH



E32771-91BC, -118BRZ
 1-Light Pendant
 Finish: See Images
 Glass: See Images
 7.5W LED (Lamps Included)
 246 Lumens
 20"/140" OAH



E32770-91BC, -118BRZ
 1-Light Wall Mount
 Finish: See Images
 Glass: See Images
 7.5W LED (Lamps Included)
 246 Lumens
 HCO: 7"





FIZZ III


This forever popular collection is now better than ever. High output LEDs now illuminate the bubble glass pendants. The LED modules produce 20% more light, 90% less heat, 25% longer life, and 75% less energy than the previous halogen lamp. You also still have dimming capability, adding a personal touch to your space.

- 3000K Color Temperature
- Ribbed Acrylic rectangular prisms with inner bubbles
- Etched Bubble Glass shades
- Standard Lutron® CL™ or Leviton Dimmers recommended

FIZZ III




E22769-89BZ, -89PC
 9-Light LED Pendant
 Finish: See Images
 Glass: Etched/Bubble
 9 x 7.5W LED (Lamps Included)
 2,214 Lumens
 135" OAH



FIZZ III



E22767-89BZ, -89PC
7-Light Pendant
Finish: See Images
Glass: Etched/Bubble
7 x 7.5W LED (Lamps Included)
1,675 Lumens
135" OAH




- 3000K Color Temperature
- Ribbed Acrylic rectangular prisms with inner bubbles
- Etched Bubble Glass shades
- Standard Lutron® CL™ or Leviton Dimmers recommended

FIZZ III




E22761-89BZ, -89PC
 1-Light Pendant
 Finish: See Images
 Glass: Etched/Bubble
 1 x 7.5W LED (Lamp Included)
 238 Lumens
 14" / 120" OAH



E22765-89BZ, -89PC
 5-Light Pendant
 Finish: See Images
 Glass: Etched/Bubble
 5 x 7.5W LED (Lamps Included)
 1,190 Lumens
 135" OAH



FIZZ III



E22764-89BZ, -89PC
5-Light Pendant
Finish: See Images
Glass: Etched/Bubble
5 x 7.5W LED (Lamps Included)
1,180 Lumens
14" / 120" OAH




- 3000K Color Temperature
- Ribbed Acrylic rectangular prisms with inner bubbles
- Etched Bubble Glass shades
- Standard Lutron® CL™ or Leviton Dimmers recommended


FIZZ III



E22760-89BZ



E22763-89BZ, -89PC
 3-Light Pendant
 Finish: See Images
 Glass: Etched/Bubble
 3 x 7.5W LED (Lamps Included)
 710 Lumens
 14" / 120" OAH



E22760-89BZ, -89PC
 1-Light Wall Mount
 Finish: See Images
 Glass: Etched/Bubble
 1 x 7.5W LED (Lamp Included)
 235 Lumens
 HCO: 7"



HILITE

These low profile pendants, featuring edge lit technology for soft even illumination, are constructed of die cast aluminum and finished in your choice of Polished Chrome or Bronze. Frosted acrylic fonts adorn the top of each pendant and are illuminated by LED, located in the top casting.




- Edge lit technology for soft even illumination
- Die cast Aluminum available in your choice of Polished Chrome or Bronze
- Frosted acrylic fonts adorn the top of each pendant, illuminated by LEDs

HILITE



E21169-01PC, -01BZ
 9-Light Pendant
 Finish: See Image
 Glass: Frosted Acrylic
 9 x 7.2W LED (Lamps Included)
 5,832 Lumens
 5.75" / 125.75" OAH





HILITE

- Edge lit technology for soft even illumination
- Die cast Aluminum available in your choice of Polished Chrome or Bronze
- Frosted acrylic fonts adorn the top of each pendant, illuminated by LEDs



E21160-01PC



6.25"

E21161-01PC, -01BZ
 1-Light Pendant
 Finish: See Image
 Glass: Frosted Acrylic
 1 x 7.2W LED (Lamp Included)
 648 Lumens
 5.75" / 125.75" OAH

5.75"

5"

7"

2.5"

7"

E21160-01PC, -01BZ
 1-Light Flush Mount/Wall Mount
 Finish: See Image
 Glass: Frosted Acrylic
 1 x 10.8W LED (Lamp Included)
 972 Lumens
 HCO: 2.4"

7"


E21162-01PC, -01BZ
 1-Light Pendant
 Finish: See Image
 Glass: Frosted Acrylic
 1 x 12W LED (Lamp Included)
 1,080 Lumens
 7" / 127" OAH

7"


HILITE



E21165-01PC



E21165-01PC, -01BZ
 5-Light Pendant
 Finish: See Image
 Glass: Frosted Acrylic
 5 x 7.2W LED (Lamps Included)
 3,240 Lumens
 5.75" / 126" OAH



E21166-01PC, -01BZ
 6-Light Pendant
 Finish: See Image
 Glass: Frosted Acrylic
 69.6W LED (Lamps Included)
 6,264 Lumens
 8.5" / 128" OAH






SOLITAIRE

Elegant beveled crystal, almond pentagone suspended inside clear glass cylinders, are brought to life by high powered 3W COB LEDs. These LEDs are cleverly concealed inside heat sink castings that are finished in Polished Chrome.

SOLITAIRE

- COB LED Technology
- 3000K Color Temperature
- CRI-80




E21116-18PC

6-Light Pendant
Finish: Polished Chrome
Glass: Clear
6 x 3W COB LED (Integrated)
1,980 Lumens
14.5" / 132" OAH



SOLITAIRE

- COB LED Technology
- 3000K Color Temperature
- CRI-80



E21115-18PC


5-Light Pendant
Finish: Polished Chrome
Glass: Clear
5 x 3W COB LED (Integrated)
1,650 Lumens
14.5" / 132" OAH




SOLITAIRE



E21113-18PC



E21113-18PC
 3-Light Pendant
 Finish: Polished Chrome
 Glass: Clear
 3 x 3W COB LED (Integrated)
 990 Lumens
 14.5" / 132" OAH



E21111-18PC
 1-Light Pendant
 Finish: Polished Chrome
 Glass: Clear
 1 x 3W COB LED (Integrated)
 330 Lumens
 14.5" / 132" OAH





POLKA


Polished Chrome hardware accentuates heavy Clear pressed glass shades with a dimple pattern. Excellent light is projected to the surface below by means of 3 watt LED modules in a soft, warm 3000K color temperature.

POLKA

- COB LED Technology
- Clear pressed glass, with a dimple pattern
- 3000K Color Temperature




E20779-18PC
9-Light Pendant
Finish: Polished Chrome
Glass: Clear
9 x 3W COB LED (Integrated)
2,970 Lumens
8" / 128" OAH



POLKA

- COB LED Technology
- Clear pressed glass, with a dimple pattern
- 3000K Color Temperature



E20775-18PC
5-Light Pendant
Finish: Polished Chrome
Glass: Clear
5 x 3W COB LED (Integrated)
1,650 Lumens
8" / 128" OAH



• Clear pressed glass, with a dimple pattern


POLKA




E20770-18PC




E20771-18PC
 1-Light Pendant
 Finish: Polished Chrome
 Glass: Clear
 1 x 3W COB LED (Integrated)
 330 Lumens
 8" / 128" OAH



E20773-18PC
 3-Light Pendant
 Finish: Polished Chrome
 Glass: Clear
 3 x 3W COB LED (Integrated)
 990 Lumens
 8" / 128" OAH



E20770-18PC
 9-Light Flush Mount
 Finish: Polished Chrome
 Glass: Clear
 9 x 3W COB LED (Integrated)
 2,970 Lumens




PUFFS

Soft forms of Matte White glass suspend from the ceiling like clouds moving through the sky. Columns of LEDs protrude down the middle of each shade to evenly illuminate the glass with a soft ambient light.



- Cloud-like forms of glass in Matte White finish
- Columns of LED inside glass provide soft, ambient light
- Available in three shapes with customizable multi-pendants
- 3000K Color Temperature
- CRI 80+


PUFFS



E21129-11WT
 14-Light Pendant
 Finish: Matte White
 Glass: Matte White
 67.2W LED PCB (Integrated)
 4,704 Lumens
 10" / 130" OAH



PUFFS




E21127-11WT

9-Light Pendant
Finish: Matte White
Glass: Matte White
43.2W LED PCB (Integrated)
3,024 Lumens
10" / 130" OAH



- Cloud-like forms of glass in Matte White finish
- Columns of LED inside glass provide soft, ambient light
- Available in three shapes with customizable multi-pendants
- 3000K Color Temperature
- CRI 80+

PUFFS




E21125-11WT
 8-Light Pendant
 Finish: Matte White
 Glass: Matte White
 38.4W LED PCB (Integrated)
 2,688 Lumens
 10" / 130" OAH



PUFFS

- Cloud-like forms of glass in Matte White finish
- Columns of LED inside glass provide soft, ambient light
- Available in three shapes with customizable multi-pendants
- 3000K Color Temperature
- CRI 80+



E21124-11WT
6-Light Pendant
Finish: Matte White
Glass: Matte White
28.8W LED PCB (Integrated)
2,016 Lumens
10" / 130" OAH



PUFFS



E21121-11WT



E21120-11WT



E21122-11WT

E21121-11WT
 1-Light Pendant
 Finish: Matte White
 Glass: Matte White
 4.8W LED PCB (Integrated)
 336 Lumens
 10" / 130" OAH

E21120-11WT
 1-Light Pendant
 Finish: Matte White
 Glass: Matte White
 4.8W LED PCB (Integrated)
 336 Lumens
 8" / 128" OAH

E21122-11WT
 1-Light Pendant
 Finish: Matte White
 Glass: Matte White
 4.8W LED PCB (Integrated)
 336 Lumens
 7.75" / 127.5" OAH





PALETTE



As if designed by Van Gogh, this collection features a flat aluminum palette, finished in Silver Foil paint. High powered 5 watt LED modules provide ample light and can be dimmed to set the mood. The ceiling fixture will work equally as well on the wall as a piece of art.

- 3000K Color Temperature
- High Powered, 5 Watt LED Modules
- Flat Aluminum palette finished in Silver Foil paint
- Dimmable
- CRI 80+

PALETTE





E20781-SF
 6-Light LED Flush/Wall Mount
 Finish: Silver Foil
 6 x 5W LED (Lamps Included)
 2,100 Lumens



E20782-SF
 9-Light LED Flush/Wall Mount
 Finish: Silver Foil
 9 x 5W LED (Lamps Included)
 2,900 Lumens



PALETTE




E20784-SF
6-Light LED Pendant
Finish: Silver Foil
6 x 5W LED (Lamps Included)
2,100 Lumens
3.25" / 124.25" OAH



- 3000K Color Temperature
- High Powered, 5 Watt LED Modules
- Flat Aluminum palette finished in Silver Foil paint
- Dimmable
- CRI 80+

PALETTE



E20785-SF
 9-Light LED Pendant
 Finish: Silver Foil
 9 x 5W LED (Lamps Included)
 2,900 Lumens
 3.25" / 124.25" OAH






PARASOL

Domes of metal rings, finished in Polished Chrome, are inset with beveled crystals to create these delicate parasols. High powered LED bulbs shine indirectly up into the inside of each shade, providing gentle illumination and vivid sparkle from the crystal.

PARASOL

- Domes of Polished Chrome rings, inset with clear, beveled crystals
- Indirect, high powered LED's provide a gentle illumination



E24499-20PC
 9-Light Pendant
 Finish: Polished Chrome
 Glass: Crystal
 9 x 4W LED (Lamps Included)
 2,880 Lumens
 8" / 128" OAH



E24496-20PC
 5-Light Pendant
 Finish: Polished Chrome
 Glass: Crystal
 5 x 4W LED (Lamps Included)
 1,600 Lumens
 8" / 128" OAH




PARASOL


- Domes of Polished Chrome rings, inset with clear, beveled crystals
- Indirect, high powered LED's provide a gentle illumination



E24493-20PC



E24495-20PC
 5-Light Pendant
 Finish: Polished Chrome
 Glass: Crystal
 5 x 4W LED (Lamps Included)
 1,600 Lumens
 8" / 128" OAH



E24493-20PC
 3-Light Pendant
 Finish: Polished Chrome
 Glass: Crystal
 3 x 4W LED (Lamps Included)
 960 Lumens
 8" / 128" OAH



PARASOL



E24497-20PC



E24491-20PC
1-Light Pendant
Finish: Polished Chrome
Glass: Crystal
1 x 4W LED (Lamp Included)
320 Lumens
8" / 128" OAH

E24497-20PC
1-Light Pendant
Finish: Polished Chrome
Glass: Crystal
1 x 15W LED (Lamp Included)
1,050 Lumens
16" / 136" OAH




JIBE

Soft rectangular forms finished in Matte White have LED boards enclosed with diffusers that are cut into the frame for a smooth and clean look. Minimalistic in its design yet technically advanced in its approach.

- Matte White finish
- Dimmable LED Boards enclosed with a diffuser
- 3000K Color Temperature
- CRI 80+

JIBE




9.5"



E23205-MW
 LED Pendant
 Finish: Matte White
 39W LED PCB (Integrated)
 2,730 Lumens
 19.75" / 122.75" OAH



JIBE



E23204-MW
LED Pendant
Finish: Matte White
26W LED PCB (Integrated)
1,820 Lumens
19.75" / 122.75" OAH



- Matte White finish
- Dimmable LED Boards enclosed with a diffuser
- 3000K Color Temperature
- CRI 80+


JIBE




E23201-MW



E23202-MW



E23201-MW
 LED Wall Mount
 Finish: Matte White
 7W LED PCB (Integrated)
 490 Lumens
 HCO: 5.75"



E23202-MW
 LED Wall Mount
 Finish: Matte White
 13W LED PCB (Integrated)
 910 Lumens
 HCO: 5.75"





PIZZAZZ


Rectangular cubes of aluminum finished in your choice of Coffee or Polished Chrome are interconnected in geometric forms. Generous amount of LED illumination filter through a sparkling Crystalline acrylic diffuser to create a spectacular display.

PIZZAZZ


- Rectangular cubes of Crystalline acrylic diffusers
- High powered LEDs deliver generous amounts of light
- 3000K Color Temperature, CRI 80+, dimmable



E24465-160COF



E24465-160COF, -160PC
 5-Light LED Pendant
 Finish: See Image
 36W LED (Intergrated)
 2,520 Lumens
 10" / 130" OAH



E24466-160COF, -160PC
 7-Light LED Pendant
 Finish: See Image
 50.4W LED (Intergrated)
 3,528 Lumens
 12" / 132" OAH




PIZZAZZ




E24467-160COF, -160PC

6-Light LED Flush Mount
 Finish: See Image
 43.2W LED (Intergrated)
 3,024 Lumens




E24468-160COF, -160PC

9-Light LED Flush Mount
 Finish: See Image
 64.8W LED (Intergrated)
 4,536 Lumens



E24469-160COF, -160PC

12-Light LED Flush Mount
 Finish: See Image
 86.4W LED (Intergrated)
 6,048 Lumens




- Rectangular cubes of Crystalline acrylic diffusers
- High powered LEDs deliver generous amounts of light
- 3000K Color Temperature, CRI 80+, dimmable



PIZZAZZ




E24461-160COF, -160PC
 1-Light LED Wall Mount
 Finish: See Image
 7.2W LED (Intergrated)
 HCO: 3.5"
 504 Lumens



E24463-160COF, -160PC
 3-Light LED Wall Mount
 Finish: See Image
 21.6W LED (Intergrated)
 HCO: 2.25"
 1,512 Lumens



E24464-160COF, -160PC
 4-Light LED Wall Mount
 Finish: See Image
 28.8W LED (Intergrated)
 HCO: 2.25"
 2,016 Lumens






BLOCS LED

The building blocks of style. This collection comes in a wide variety of applications for the most innovative illumination solutions. The lamp configurations boast thick, Clear/Frosted square glasses encasing G9 LED bulbs. Light blocks are anchored to a highly reflective Polished Chrome frame that reflects their simple elegance.

BLOCS LED

- Dimmable G9 LED bulbs included
- Thick glass blocks with frosted openings
- 3000K Color Temperature, CRI 80+, dimmable



E32036-18PC

8-Light LED Pendant
Finish: Polished Chrome
Glass: Clear/Frosted
17.6W LED (Lamps Included)
3,520 Lumens
12" / 118" OAH




BLOCS LED


- Dimmable G9 LED bulbs included
- Thick glass blocks with frosted openings
- 3000K Color Temperature, CRI 80+, dimmable




E32038-18PC



E32034-18PC



E32034-18PC
 6-Light LED Pendant
 Finish: Polished Chrome
 Glass: Clear/Frosted
 13.2W LED (Lamps Included)
 2,640 Lumens
 12" / 118" OAH




E32038-18PC
 4-Light LED Flush Mount
 Finish: Polished Chrome
 Glass: Clear/Frosted
 8.8W LED (Lamps Included)
 1,760 Lumens




BLOCS LED




E32031-18PC
 1-Light LED Wall Mount
 Finish: Polished Chrome
 Glass: Clear/Frosted
 2.2W LED (Lamps Included)
 440 Lumens
 HCO: 3.5"




E32032-18PC
 2-Light LED Wall Mount
 Finish: Polished Chrome
 Glass: Clear/Frosted
 4.4W LED (Lamps Included)
 880 Lumens
 HCO: 3.5"




E32033-18PC
 3-Light LED Bath Vanity
 Finish: Polished Chrome
 Glass: Clear/Frosted
 6.6W LED (Lamps Included)
 1,320 Lumens
 HCO: 3.5"



E32170-18PC
 4-Light LED Bath Vanity
 Finish: Polished Chrome
 Glass: Clear/Frosted
 8.8W LED (Lamps Included)
 1,760 Lumens
 HCO: 3.5"




E32171-18PC
 5-Light LED Bath Vanity
 Finish: Polished Chrome
 Glass: Clear/Frosted
 11W LED (Lamps Included)
 2,200 Lumens
 HCO: 3.5"




FIZZ III





E22751-89PC
 2-Light Bath Vanity
 Finish: Polished Chrome
 Glass: Etched/Bubble
 2 x 3W LED (Lamps Included)
 420 Lumens
 HCO: 2.5"




E22752-89PC
 4-Light Bath Vanity
 Finish: Polished Chrome
 Glass: Etched/Bubble
 4 x 3W LED (Lamps Included)
 840 Lumens
 HCO: 2.5"



E22753-89PC
 6-Light Bath Vanity
 Finish: Polished Chrome
 Glass: Etched/Bubble
 6 x 3W LED (Lamps Included)
 1,260 Lumens
 HCO: 2.5"



E22754-89PC
 8-Light Bath Vanity
 Finish: Polished Chrome
 Glass: Etched/Bubble
 8 x 3W LED (Lamps Included)
 1,680 Lumens
 HCO: 2.5"





- Suitable for Damp Location
- ADA Approved



FIZZ III




E22755-89PC
 2-Light Bath Vanity
 Finish: Polished Chrome
 Glass: Etched/Bubble
 2 x 3W LED (Lamps Included)
 420 Lumens



E22756-89PC
 2-Light Bath Vanity
 Finish: Polished Chrome
 Glass: Etched/Bubble
 2 x 15W LED (Lamps Included)
 2,100 Lumens



E22757-89PC
 2-Light Bath Vanity
 Finish: Polished Chrome
 Glass: Etched/Bubble
 2 x 22W LED (Lamps Included)
 3,000 Lumens



GEM

With the illusion of floating on air, the Gem Collection offers a touch of mystery to any room. Intertwined metal cubes are encased by clear crystal cubes, allowing xenon light to shine from within and bursting out through the embellished crystal.


- Standard Dimmable
- G9, Xenon lamps Included




E22836-18PCPC



E22838-18PCPC



E22836-18SVPC, -18PCPC
 6-Light Flush Mount
 Finish: Polished Chrome
 Glass: Clear
 6 x 40W G9 (Lamps Included)
 3,000 Lumens




E22838-18SVPC, -18PCPC
 4-Light Flush Mount
 Finish: Polished Chrome
 Glass: Clear
 4 x 40W G9 (Lamps Included)
 2,000 Lumens







E22830-18SVPC, -18PCPC
 1-Light Wall Mount
 Finish: Polished Chrome
 Glass: Clear
 1 x 40W G9 (Lamp Included)
 500 Lumens
 HCO: 2"




E22832-18SVPC, -18PCPC
 2-Light Bath Vanity
 Finish: Polished Chrome
 Glass: Clear
 2 x 40W G9 (Lamps Included)
 1,000 Lumens
 HCO: 2"



E22833-18SVPC, -18PCPC
 3-Light Bath Vanity
 Finish: Polished Chrome
 Glass: Clear
 3 x 40W G9 (Lamps Included)
 1,500 Lumens
 HCO: 2"



E22834-18SVPC, -18PCPC
 4-Light Bath Vanity
 Finish: Polished Chrome
 Glass: Clear
 4 x 40W G9 (Lamps Included)
 2,000 Lumens
 HCO: 2"



E22835-18SVPC, -18PCPC
 5-Light Bath Vanity
 Finish: Polished Chrome
 Glass: Clear
 5 x 40W G9 (Lamps Included)
 2,500 Lumens
 HCO: 2"



RONDELLE

Inspired by the small disks of glass that are used as ornaments in stained glass windows, the Rondelle single light White or Red pendants presents a simple and clean cylindrical form. The Rondelle possess matching glass canopy accented by Polished Chrome hardware and featuring adjustable height for maximum adaptability. Consider it the perfect lighting solution for bar, bathroom, kitchen island or pool table.



E20841-01, -03
 1-Light Pendant
 Finish: Polished Chrome
 Glass: See Images
 1 x 60W MB Lamp
 672 Lumens
 24" / 120" OAH

• Matching glass canopy

12"
3.5"

CAPS

Bold color combined with simple curves defines the essence of the Caps collection. The exquisite pendants with matching glass canopy of Caps are available in White and Red. Equally suited for residential or commercial applications, you can either arrange the pendants flying solo or in multiple formations.



E20851-01, -03
 1-Light Pendant
 Finish: Polished Chrome
 Glass: See Images
 1 x 100W MB Lamp
 1,150 Lumens
 18" / 120" OAH

• Matching glass canopy

7"
8" Dia.

CILANDRO LED

This ever popular collection is now available in LED. Four integrated LED boards are enclosed with a commercial grade dimmable driver for ultimate function and long life. Great for commercial or residential applications, Matte White glass twist locks into a steel base finished in Satin Nickel for a clean modern look.


- 3000K Color Temperature
- Four integrated LED boards enclosed with a commercial grade dimmable driver
- Matte White glass twist locks into a steel base
- CRI 80




E63106-11SN



E63107-11SN




E63109-11SN




E63106-11SN
LED Wall Mount
Finish: Satin Nickel
Glass: Matte White
4 x 2.4W LED (Lamp Included)
672 Lumens
HCO:10"

- Glass is enclosed
- Suitable for Damp location



E63107-11SN
LED Wall Mount
Finish: Satin Nickel
Glass: Matte White
8 x 2.4W LED (Lamp Included)
1,344 Lumens
HCO:2.5"

- Glass is enclosed
- Suitable for Damp location



E63109-11SN
LED Pendant
Finish: Satin Nickel
Glass: Matte White
4 x 2.4W LED (Lamp Included)
672 Lumens
24" / 134" OAH

- Glass is enclosed
- Dry Location only




STAGE

Inspired by stage lighting, this functional collection will display plenty of light wherever needed. This refined rendition features a soft round body finished in Satin Aluminum, Chrome hardware accents, and is powered by a dimmable 15 watt COB LED.




E20833-SA
LED Pendant
Finish: Satin Aluminum
1 x 15W COB LED (Integrated)
1,650 Lumens
22" / 142" OAH




- COB technology
- Dimmable 15 watt LED
- Satin Aluminum finish, Chrome hardware accents
- 3000K Color Temperature

STAGE





E20835-SA
LED Floor Lamp
Finish: Satin Aluminum
1 x 15W COB LED (Integrated)
1,650 Lumens


- Not Dimmable



E20831-SA
LED Semi Flushmount
Finish: Satin Aluminum
1 x 15W COB LED (Integrated)
1,650 Lumens



• Satin Aluminum finish



• Chrome hardware accent



INCA

Legendary meets contemporary with the Inca Collection. Reminiscent of the mythical tales of Incan treasures, the fixtures offer brilliantly shining crystal enclosed within a precision laser-cut sheath that cannot be duplicated. The glow of the LED light from within casts a beautifully radiant shine that adorns the outer permeable layer.

- 304 Grade Stainless Steel
- Features a White Acrylic liner and diffuser
- Suitable for Indoor and Outdoor locations
- 3000K Color Temperature


INCA

FOR WET LOCATION LED




E21336-61BZ, -61PC
 4-Light LED Large Wall Sconce
 Finish: See Images
 Glass: Acrylic
 4 x 6W LED (Lamps Included)
 1,280 Lumens

- Made with Steel grade 304
- Suitable for Indoor or Outdoor Locations




E21335-61BZ, -61PC
 4-Light LED Medium Wall Sconce
 Finish: See Images
 Glass: Acrylic
 4 x 6W LED (Lamps Included)
 1,280 Lumens


- Made with Steel grade 304
- Suitable for Indoor or Outdoor Locations



E21333-61BZ, -61PC
 2-Light LED Small Wall Sconce
 Finish: See Images
 Glass: Acrylic
 2 x 6W LED (Lamps Included)
 640 Lumens

- Made with Steel grade 304
- Suitable for Indoor or Outdoor Locations







ALUMILUX LED

The Alumilux collection of high quality wall sconces are sure to impress. European inspired design, machined out of blocks of solid Aluminum, give these sconces both the look and quality expected for the discriminate buyer. High powered LEDs drive the light in dramatic fashion and many are approved for wet location applications.


- Machined Aluminum
- Intergrated LED
- 3000K Color Temperature
- CRI 80

ALUMILUX LED





E41374-AL, -BZ
 LED Outdoor Wall Mount
 Finish: See Image
 4W LED (Integrated)
 280 Lumens
 HCO: 2.25"

- Adjustable
- Indirect



E41376-WT
 LED Wall Mount
 Finish: White
 4W LED (Integrated)
 280 Lumens
 HCO: 3"

- Indoor Only
- Indirect



E41378-WT
 LED Wall Mount
 Finish: White
 5W LED (Integrated)
 350 Lumens
 HCO: 4.5"

- Indoor Only
- Indirect



ALUMILUX LED



E41380-BZ



E41381-WT




E41382-WT

• Shown with lights on




E41380-BZ, -WT
LED Outdoor Wall Mount
Finish: See Image
6W LED (Integrated)
420 Lumens
HCO: 2.75"

• Backlit Indirect




E41382-BZ, -WT
LED Outdoor Wall Mount
Finish: See Image
15W LED (Integrated)
1,050 Lumens
HCO: 6"

• Backlit Indirect



E41381-BZ, -WT
LED Outdoor Wall Mount
Finish: See Image
8W LED (Integrated)
560 Lumens
HCO: 3.5"

• Backlit Indirect




- Machined Aluminum
- Intergrated LED
- 3000K Color Temperature
- CRI 80

ALUMILUX LED




E41386-AL

E41386-AL, -WT
 LED Outdoor Wall Mount
 Finish: See Image
 4W LED (Intergrated)
 280 Lumens
 HCO: 2.25"




E41388-WT

E41388-AL, -WT
 LED Outdoor Wall Mount
 Finish: See Image
 10W LED (Integrated)
 700 Lumens
 HCO: 3"



E41385-WT

E41385-WT
 LED Outdoor Wall Mount
 Finish: White
 5W LED (Integrated)
 350 Lumens
 HCO: 4.25"



• Shown with lights on



INDEX

E20171.....	75	E20903.....	113	E21166.....	142
E20172.....	75	E20904.....	114	E21169.....	140
E20173.....	75	E20905.....	113	E21172.....	4
E20175.....	73	E20906.....	112	E21174.....	4
E20177.....	74	E20908.....	112	E21176.....	3
E20225.....	58	E21026.....	84	E21178.....	2
E20226.....	57	E21028.....	84	E21333.....	186
E20638.....	128	E21059.....	110	E21335.....	186
E20639.....	128	E21111.....	146	E21336.....	186
E20691.....	88	E21113.....	146	E21399.....	106
E20693.....	88	E21115.....	145	E21401.....	106
E20695.....	87	E21116.....	144	E21403.....	106
E20697.....	86	E21120.....	156	E21405.....	105
E20770.....	150	E21121.....	156	E21406.....	104
E20771.....	150	E21122.....	156	E21409.....	105
E20773.....	150	E21124.....	155	E21410.....	20
E20775.....	149	E21125.....	154	E21415.....	19
E20779.....	148	E21127.....	153	E21417.....	18
E20781.....	158	E21129.....	152	E21510.....	44
E20782.....	158	E21140.....	82	E21513.....	44
E20784.....	159	E21141.....	82	E21515.....	43
E20785.....	160	E21142.....	81	E22405.....	55
E20831.....	184	E21144.....	81	E22407.....	54
E20833.....	183	E21146.....	80	E22408.....	56
E20835.....	184	E21148.....	82	E22453.....	60
E20841.....	181	E21160.....	141	E22455.....	60
E20851.....	181	E21161.....	141	E22456.....	60
E20901.....	114	E21162.....	141	E22572.....	28
E20902.....	113	E21165.....	142	E22574.....	28

INDEX

E22576.....	26	E22832.....	180	E23094.....	24
E22578.....	27	E22833.....	180	E23096.....	23
E22591.....	102	E22834.....	180	E23098.....	22
E22596.....	102	E22835.....	180	E23201.....	168
E22599.....	101	E22836.....	179	E23202.....	168
E22710.....	120	E22838.....	179	E23204.....	167
E22712.....	120	E22840.....	124	E23205.....	166
E22713.....	119	E22841.....	124	E24048.....	50
E22714.....	118	E22843.....	124	E24049.....	49
E22715.....	117	E22845.....	123	E24120.....	68
E22716.....	116	E22847.....	122	E24122.....	68
E22751.....	177	E22848.....	123	E24124.....	68
E22752.....	177	E22849.....	122	E24125.....	67
E22753.....	177	E22864.....	72	E24127.....	66
E22754.....	177	E22866.....	71	E24284.....	12
E22755.....	178	E22891.....	96	E24286.....	12
E22756.....	178	E22892.....	96	E24295.....	42
E22757.....	178	E22893.....	96	E24296.....	41
E22760.....	138	E22894.....	96	E24297.....	42
E22761.....	136	E22896.....	96	E24363.....	100
E22763.....	138	E22897.....	94	E24365.....	99
E22764.....	137	E22898.....	93	E24367.....	98
E22765.....	136	E22899.....	95	E24461.....	172
E22767.....	135	E22902.....	126	E24463.....	172
E22769.....	134	E22904.....	126	E24464.....	172
E22820.....	70	E22906.....	125	E24465.....	170
E22822.....	70	E23073.....	52	E24466.....	170
E22824.....	69	E23077.....	52	E24467.....	171
E22830.....	180	E23091.....	24	E24468.....	171

INDEX

E24469.....	171	E24571.....	108	E41381.....	189
E24491.....	164	E24573.....	108	E41382.....	189
E24493.....	163	E24580.....	48	E41385.....	190
E24495.....	163	E24582.....	48	E41386.....	190
E24496.....	162	E24584.....	47	E41388.....	190
E24497.....	164	E24586.....	46	E41390.....	63
E24499.....	162	E24670.....	92	E41392.....	64
E24512.....	15	E24672.....	92	E41394.....	64
E24514.....	15	E24674.....	91	E41396.....	62
E24516.....	14	E24676.....	90	E41398.....	63
E24522.....	16	E32031.....	176	E41430.....	10
E24524.....	16	E32032.....	176	E41432.....	10
E24526.....	16	E32033.....	176	E41433.....	9
E24531.....	78	E32034.....	175	E41435.....	9
E24532.....	78	E32036.....	174	E41436.....	8
E24533.....	78	E32038.....	175	E41437.....	7
E24541.....	34	E32170.....	176	E41438.....	6
E24546.....	34	E32171.....	176	E63106.....	182
E24550.....	40	E32770.....	132	E63107.....	182
E24551.....	40	E32771.....	132	E63109.....	182
E24552.....	38	E32774.....	132		
E24553.....	38	E32775.....	130		
E24554.....	36	E32776.....	131		
E24555.....	37	E32778.....	130		
E24557.....	39	E32779.....	131		
E24562.....	32	E41374.....	188		
E24564.....	32	E41376.....	188		
E24566.....	31	E41378.....	188		
E24568.....	30	E41380.....	189		

FINISHES, SHADES

Code	Finish
AL	Aluminum
BC	Black Chrome
BK	Black
BR	Brick
BRZ	Anodized Bronze
BZ	Bronze
BZPL	Bronze / Platinum
CHP	Champagne
COF	Coffee
DG	Dark Grey
GM	Gunmetal
MS	Metallic Silver
MW	Matte White
NWD	Natural Wood
OI	Oil Rubbed Bronze
PC	Polished Chrome
PCBK	Polished Chrome / Black
PCWT	Polished Chrome/White
PL	Platinum
PLPC	Platinum / Polished Chrome
SA	Satin Aluminum
SB	Steel Blue
SC	Brushed Copper
SF	Silver Foil
SN	Satin Nickel
SST	Stainless Steel
SV	Silver
WT	White

Code	Shade
69	Silver Plated
78	Mesh
93	Aluminum/Red
94	Aluminum/Green
97	Black Chain
120	Silver Sheer
AL	Aluminum
BR	Brushed Aluminum
GC	Grass Cloth
PC	Polished Chrome
SW	Steel Web
WL	White Linen
WW	White Weave

GLASS
















Code	Glass
01	White
02	Black
03	Red
04	Green
05	Amber
08	Red Gloss
09	Frost White
10	Clear/White
11	Matte White
13	White Ripple
14	Amber Ripple
18	Clear
19	Lead - Glass
20	Crystal
24	Clear
25	Clear/Amber
26	Amber Murano
28	Clear Murano
39	Grey Ripple
50	Black Amber Swirl
51	Black Zebra
53	Conch
54	Translucent Frost
56	Chocolate Mousse
61	White
69	Silver Plate
75	Clear Acrylic
78	Mesh
79	Threaded
81	Mirror Chrome
83	Clear Acrylic
85	Opal White
86	Frosted Speckled












Code	Glass
87	Chocolate Swirl
88	Snow White
89	Etched/Bubble
90	Frosted
91	Bubble
93	Clear/Frosted
94	Cognac
101	White Lava
102	Amber Lava
103	Gold Lava
104	Amber Leopard
105	White Leopard
106	Amber Cloud
107	Cherry Swirl
108	Grape Swirl
109	Tangerine Swirl
111	Red Spiral
112	White Spiral
113	White Cirrus
114	Sunset
118	Champagne
132	Sky Blue
136	Champagne
138	Smoke
140	Graduating Blue
141	Graduating Amber
142	Graduating Smoke
146	Clear/Mirror
148	Multi Color
151	Mirror Copper
160	Crystalline
FT	Frosted

REPLACEMENT BULBS

Type	Base	Watts	Item	Description
CF	2G11	18	BUCF-FT18-2G11-830	18W CFL Twin 4 Pin 2G11 Bulb 3000K
CF	2G11	36	BUCF-FT36-2G11-830	36W CFL Twin 4 Pin 2G11 Bulb 3000K
CF	G24q-1	13	BUCF-CFQ13-G24Q-1-827	13W CFL Quad 4 Pin G24q-1 Bulb 2700K
CF	G24q-2	18	BUCF-CFQ18-G24Q-2-827	18W CFL Quad 4 Pin G24q-2 Bulb 2700K
CF	G24q-3	26	BUCF-CFQ26-G24Q-3-827	26W CFL Quad 4 Pin G24q-3 Bulb 2700K
CF	G24q-3	26	BUCF-CFQ26-G24Q-3-830	26W CFL Quad 4 Pin G24q-3 Bulb 3000K
CF	GX23-2	13	BUCF-CFQ13-GX23-2-827	13W CFL Quad Bi-Pin GX23-2 Bulb 2700K
F	GU24	13	BUF-SP13-GU24-827	13W FL Spiral GU24 Bulb 2700K
F	GU24	13	BUF-SPLP13-GU24-827	13W FL Low Profile Spiral GU24 Bulb 2700K
F	GU24	18	BUF-SP18-GU24-827	18W FL Spiral GU24 Bulb 2700K
F	GU24	18	BUF-SPLP18-GU24-827	18W FL Low Profile Spiral GU24 Bulb 2700K
F	GU24	26	BUF-SP26-GU24-827	26W FL Spiral GU24 Bulb 2700K
F	T5	13	BUF-F13T5-831	13W FL T5 Linear Mini Bi-Pin Bulb 3100K 21"L
F	T5	16	BUF-F16T5-831	16W FL T5 Linear Mini Bi-Pin Bulb 3100K 23.5"L
F	T5	21	BUF-F21T5-827	21W FL T5 Linear Mini Bi-Pin Bulb 2700K 34"L
F	T5	21	BUF-F21T5-830	21W FL T5 Linear Mini Bi-Pin Bulb 3000K 34"L
F	T5	24	BUF-F24T5-835	24W FL T5 Linear Mini Bi-Pin Bulb 3500K 22"L
F	T5	26	BUF-F26T5-831	26W FL T5 Linear Mini Bi-Pin Bulb 3100K 41.5"L
F	T5	39	BUF-F39T5-835	39W FL T5 Linear Mini Bi-Pin Bulb 3500K 34"L
F	T5	8	BUF-F8T5-831	8W FL T5 Linear Mini Bi-Pin Bulb 3100K
F	T9	22	BUF-FC8T9-WW	22W FL T9 Circline 4 Pin Bulb 2700K
F	T9	32	BUF-FC12T9-WW	32W FL T9 Circline 4 Pin Bulb 2700K
F	T9	40	BUF-FC16T9-WW	40W FL T9 Circline 4 Pin Bulb 3100K
H	E26	50	BUH-50W-PAR20-FL-CL-120V	50W Halogen PAR20 120V Bulb Clear
H	GU10	35	BUH-35W-GU10-CL-120V	35W Halogen GU10 110-130V Bulb Clear
H	GU10	50	BUH-50W-GU10-CL-120V	50W Halogen GU10 110-130V Bulb Clear
I	E26	40	BUI-40W-T10-E26-IF-120V	40W Incandescent MB T10 120V Bulb Inside Frost
I	E26	60	BUI-60W-ST64-E26-CL-120V	60W Incandescent MB ST64 120V Bulb Clear
I	E26	60	BUI-60W-T10-E26-IF-120V	60W Incandescent MB T10 120V Bulb Inside Frost
L	E12	4	BUL-4W-E12-T-CL-120V-827	LED Filament 4W E12 Candelabra 2700K
L	G3	0.2	BUL-.2W-G3-CL-12V	.2W LED G3 12V 3500K Bulb Clear
L	G4	1.5	BUL-1.5W-G4-CL-12V	1.5W LED G4 12V 3000K Bulb Clear (See Supp Descr)
L	G9	2.3	BUL-2.3W-G9-CL-120V-830	2.3W LED G9 3000K 120V Bulb Clear
L	G9	2.9	BUL-2.9W-G9-CL-120V-827	2.9W LED G9 2700K 120V Bulb Clear
L	G9	2.9	BUL-2.9W-G9-CL-120V-835	2.9W LED G9 3500K 120V Bulb Clear
L	GU10	4	BUL-4W-GU10-CL-120V	4W Dimmable LED GU10 3500K 120V Bulb Clear
L	GU10	5	BUL-5W-GU10-FT-120V-830	5W Dimmable LED GU10 3000K 120V Bulb Clear
L	GU24	11	BUL-11W-GU24-CL-120V-830	11W LED GU24 3000K 120V Clear
L	GU24	7	BUL-7W-GU24-CL-120V-830	7W LED GU24 3000K 120V Clear
L	GU24	9	BUL-9W-GU24-FT-120V-830	9W Dimmable LED GU24 3000K 120V Bulb Frosted
L	MR11	3	BUL-3W-MR11-CL-12V	3W LED MR11 12V 3000K Bulb Clear
L	MR16	3	BUL-3W-MR16-FL-CL-12V	3W LED MR16 3000K 12V Bulb Clear
L	MR16	7	BUL-7W-MR16-FL-CL-12V	7W LED MR16 3000K 12V Clear
L	PAR30	11	BUL-11W-PAR30-CL-120V-830	11W Dimmable LED PAR30 3000K 120V
L	PAR38	16	BUL-16W-PAR38-CL-120V-830	16W Dimmable LED PAR38 3000K 120V
X	G4	10	BUX-10W-G4-CL-12V	10W Xenon Bi-Pin G4 12V Bulb Clear
X	G4	10	BUX-10W-G4-FT-12V	10W Xenon Bi-Pin G4 12V Bulb Frosted
X	G4	20	BUX-20W-G4-CL-12V	20W Xenon Bi-Pin G4 12V Bulb Clear
X	G4	20	BUX-20W-G4-FT-12V	20W Xenon Bi-Pin G4 12V Bulb Frosted
X	G4	35	BUX-35W-G4-CL-12V	35W Xenon Bi-Pin G4 12V Bulb Clear
X	G6.35	35	BUX-35W-G6.35-CL-12V	35W Xenon Bi-Pin G6.35 12V Bulb Clear
X	G6.35	35	BUX-35W-G6.35-FT-12V	35W Xenon Bi-Pin G6.35 12V Bulb Frosted
X	G6.35	50	BUX-50W-G6.35-CL-12V	50W Xenon Bi-Pin G6.35 12V Bulb Clear
X	G6.35	50	BUX-50W-G6.35-FT-12V	50W Xenon Bi-Pin G6.35 12V Bulb Frosted
X	G8	20	BUX-20W-G8-CL-120V	20W Xenon Bi-Pin G8 120V Bulb Clear
X	G9	25	BUX-25W-G9-CL-120V	25W Xenon Bi-Pin G9 120V Bulb Clear
X	G9	25	BUX-25W-G9-FT-120V	25W Xenon Bi-Pin G9 120V Bulb Frosted
X	G9	40	BUX-40W-G9-CL-120V	40W Xenon Bi-Pin G9 120V Bulb Clear
X	G9	40	BUX-40W-G9-FT-120V	40W Xenon Bi-Pin G9 120V Bulb Frosted
X	G9	50	BUX-50W-G9-CL-120V	50W Xenon Bi-Pin G9 120V Bulb Clear
X	G9	50	BUX-50W-G9-FT-120V	50W Xenon Bi-Pin G9 120V Bulb Frosted
X	G9	60	BUX-60W-G9-CL-120V	60W Xenon Bi-Pin G9 120V Bulb Clear
X	G9	60	BUX-60W-G9-FT-120V	60W Xenon Bi-Pin G9 120V Bulb Frosted
X	G9	75	BUX-75W-G9-CL-120V	75W Xenon Bi-Pin G9 120V Bulb Clear
X	G9	75	BUX-75W-G9-FT-120V	75W Xenon Bi-Pin G9 120V Bulb Frosted
X	WEDGE	18	BUX-18W-WEDGE-CL-12V	18W Xenon Xelogen Wedge 12V Bulb Clear

LAMPING GUIDE

Linedrawings	Item	Type	Base	Watt	Description
	BUCF-FT18-2G11-830	CF	2G11	18	18W CFL Twin 4 Pin 2G11 Bulb 3000K
	BUCF-FT36-2G11-830	CF	2G11	36	36W CFL Twin 4 Pin 2G11 Bulb 3000K
	BUCF-CFQ13-G24Q-1-827	CF	G24q-1	13	13W CFL Quad 4 Pin G24q-1 Bulb 2700K
	BUCF-CFQ18-G24Q-2-827	CF	G24q-2	18	18W CFL Quad 4 Pin G24q-2 Bulb 2700K
	BUCF-CFQ26-G24Q-3-827	CF	G24q-3	26	26W CFL Quad 4 Pin G24q-3 Bulb 2700K
	BUCF-CFQ26-G24Q-3-830	CF	G24q-3	26	26W CFL Quad 4 Pin G24q-3 Bulb 3000K
	BUCF-CFQ13-GX23-2-827	CF	GX23-2	13	13W CFL Quad Bi-Pin GX23-2 Bulb 2700K
	BUF-SP13-GU24-827	F	GU24	13	13W FL Spiral GU24 Bulb 2700K
	BUF-SP18-GU24-827	F	GU24	18	18W FL Spiral GU24 Bulb 2700K
	BUF-SP26-GU24-827	F	GU24	26	26W FL Spiral GU24 Bulb 2700K
	BUF-SPLP13-GU24-827	F	GU24	13	13W FL Low Profile Spiral GU24 Bulb 2700K
	BUF-SPLP18-GU24-827	F	GU24	18	18W FL Low Profile Spiral GU24 Bulb 2700K
	BUF-F13T5-831	F	T5	13	13W FL T5 Linear Mini Bi-Pin Bulb 3100K 21"L
	BUF-F16T5-831	F	T5	16	16W FL T5 Linear Mini Bi-Pin Bulb 3100K 23.5"L
	BUF-F21T5-827	F	T5	21	21W FL T5 Linear Mini Bi-Pin Bulb 2700K 34"L
	BUF-F21T5-830	F	T5	21	21W FL T5 Linear Mini Bi-Pin Bulb 3000K 34"L
	BUF-F24T5-835	F	T5	24	24W FL T5 Linear Mini Bi-Pin Bulb 3500K 22"L
	BUF-F26T5-831	F	T5	26	26W FL T5 Linear Mini Bi-Pin Bulb 3100K 41.5"L
	BUF-F39T5-835	F	T5	39	39W FL T5 Linear Mini Bi-Pin Bulb 3500K 34"L
	BUF-F8T5-831	F	T5	8	8W FL T5 Linear Mini Bi-Pin Bulb 3100K
	BUF-FC8T9-WW	F	T9	22	22W FL T9 Circline 4 Pin Bulb 2700K
	BUF-FC12T9-WW	F	T9	32	32W FL T9 Circline 4 Pin Bulb 2700K
	BUF-FC16T9-WW	F	T9	40	40W FL T9 Circline 4 Pin Bulb 3100K
	BUH-50W-PAR20-FL-CL-120V	H	E26	50	50W Halogen PAR20 120V Bulb Clear
	BUH-35W-GU10-CL-120V	H	GU10	35	35W Halogen GU10 110-130V Bulb Clear
	BUH-50W-GU10-CL-120V	H	GU10	50	50W Halogen GU10 110-130V Bulb Clear
	BUI-40W-T10-E26-IF-120V	I	E26	40	40W Incandescent MB T10 120V Bulb Inside Frost
	BUI-60W-T10-E26-IF-120V	I	E26	60	60W Incandescent MB T10 120V Bulb Inside Frost
	BUI-60W-ST64-E26-CL-120V	I	E26	60	60W Incandescent MB ST64 120V Bulb Clear
	BUL-4W-E12-T-CL-120V-827	L	E12	4	LED Filament 4W E12 Candelabra 2700K
	BUL-.2W-G3-CL-12V	L	G3	0.2	.2W LED G3 12V 3500K Bulb Clear
	BUL-1.5W-G4-CL-12V	L	G4	1.5	1.5W LED G4 12V 3000K Bulb Clear (See Supp Descr)
	BUL-2.3W-G9-CL-120V-835	L	G9	2.3	2.3W LED G9 3500K 120V Bulb Clear
	BUL-2.9W-G9-CL-120V-827	L	G9	2.9	2.9W LED G9 2700K 120V Bulb Clear
	BUL-2.9W-G9-CL-120V-835	L	G9	2.9	2.9W LED G9 3500K 120V Bulb Clear

Linedrawings	Item	Type	Base	Watt	Description
	BUL-5W-GU10-FT-120V-830	L	GU10	5	5W Dimmable LED GU10 3000K 120V Bulb Clear
	BUL-11W-GU24-CL-120V-830	L	GU24	11	11W LED GU24 3000K 120V Clear
	BUL-7W-GU24-CL-120V-830	L	GU24	7	7W LED GU24 3000K 120V Clear
	BUL-9W-GU24-FT-120V-830	L	GU24	9	9W Dimmable LED GU24 3000K 120V Bulb Frosted
	BUL-3W-MR11-CL-12V	L	MR11	3	3W LED MR11 12V 3000K Bulb Clear
	BUL-3W-MR16-FL-CL-12V	L	MR16	3	3W LED MR16 3000K 12V Bulb Clear
	BUL-7W-MR16-FL-CL-12V	L	MR16	7	7W LED MR16 3000K 12V Clear
	BUL-11W-PAR30-CL-120V-830	L	PAR30	11	11W Dimmable LED PAR30 3000K 120V
	BUL-16W-PAR38-CL-120V-830	L	PAR38	16	16W Dimmable LED PAR38 3000K 120V
	BUX-10W-G4-CL-12V	X	G4	10	10W Xenon Bi-Pin G4 12V Bulb Clear
	BUX-10W-G4-FT-12V	X	G4	10	10W Xenon Bi-Pin G4 12V Bulb Frosted
	BUX-20W-G4-CL-12V	X	G4	20	20W Xenon Bi-Pin G4 12V Bulb Clear
	BUX-20W-G4-FT-12V	X	G4	20	20W Xenon Bi-Pin G4 12V Bulb Frosted
	BUX-35W-G4-CL-12V	X	G4	35	35W Xenon Bi-Pin G4 12V Bulb Clear
	BUX-35W-G6.35-CL-12V	X	G6.35	35	35W Xenon Bi-Pin G6.35 12V Bulb Clear
	BUX-35W-G6.35-FT-12V	X	G6.35	35	35W Xenon Bi-Pin G6.35 12V Bulb Frosted
	BUX-50W-G6.35-CL-12V	X	G6.35	50	50W Xenon Bi-Pin G6.35 12V Bulb Clear
	BUX-50W-G6.35-FT-12V	X	G6.35	50	50W Xenon Bi-Pin G6.35 12V Bulb Frosted
	BUX-20W-G8-CL-120V	X	G8	20	20W Xenon Bi-Pin G8 120V Bulb Clear
	BUX-25W-G9-CL-120V	X	G9	25	25W Xenon Bi-Pin G9 120V Bulb Clear
	BUX-25W-G9-FT-120V	X	G9	25	25W Xenon Bi-Pin G9 120V Bulb Frosted
	BUX-40W-G9-CL-120V	X	G9	40	40W Xenon Bi-Pin G9 120V Bulb Clear
	BUX-40W-G9-FT-120V	X	G9	40	40W Xenon Bi-Pin G9 120V Bulb Frosted
	BUX-50W-G9-CL-120V	X	G9	50	50W Xenon Bi-Pin G9 120V Bulb Clear
	BUX-50W-G9-FT-120V	X	G9	50	50W Xenon Bi-Pin G9 120V Bulb Frosted
	BUX-18W-WEDGE-CL-12V	X	WEDGE	18	18W Xenon Xelogen Wedge 12V Bulb Clear

Bulb Type Glossary

CF - Compact Fluorescent
 F - Fluorescent
 H - Halogen

I - Incandescent
 L - LED
 X - Xenon

Warranty and Other Information

- For specific and detailed warranty information, ask your ET2 Contemporary Lighting sales representative or visit www.et2online.com/warranty.
- ET2 Contemporary Lighting reserves the right to change details of design, materials, colors and finishes. Color may vary from what is pictured due to limitations inherent to the photographic process.
- Always consult a qualified, licensed electrician before installation of any product weighing 35 pounds or more. We recommend that a qualified, licensed electrician do installations. Always install to a mechanically sound structure.
- Products in this supplement are UL or ETL certified. All electrical products are certified and listed to standards for use in the United States of America or Canada.
- Lamps are not included unless otherwise noted.
- Printed in China



ET2 Contemporary Lighting is a trademark of Maxim Lighting International, Inc.

StarStrand and CounterMax are registered trademarks of Maxim Lighting International, Inc.

All designs, logos, products and images © Copyright 2016 ET2 Contemporary Lighting.

All Rights Reserved.

#ET2lighting





Contemporary Lighting™

LETCAT1606
\$5.00



ET2 Contemporary Lighting

253 North Vineland Avenue
City of Industry, California
91746
USA

General Info: 626.956.4200
Customer Service: 800.486.2946
General Fax: 626.956.4226

Dallas Trade Mart: 214.748.8455
Showroom: 3901
Email: info@et2online.com
Web: www.et2online.com

#ET2lighting



ET2 Contemporary Lighting and all designs,
logos and images © 2016 ET2 Contemporary
Lighting. All Rights Reserved.