

CIRCUIT BREAKERS

Hinged Single-Pole Breaker Lockout



- Hinged single-pole lockout with locking post design for breakers with “holes” in the trip lever. Locks lever in off position to isolate and prevent breaker use
- Ideal for applications where panel closure is preferred

| Description | Qty./Card | Cat. No. |
|------------------------------------|-----------|----------|
| Hinged Single-Pole Breaker Lockout | 3 | 44-810 |
| Hinged Single-Pole Breaker Lockout | 100 | 44-1810 |

Universal Multi-Pole Breaker Lockout



- Works with most major multi-pole breakers with tie-bar type switches including GE, ITE Sylvania, Challenger, Bryant, Westinghouse, Square D (½ poles) and General Switch Co.
- Easy to install — thumbscrew secures and locks tie bar in place; no cable ties or tools required

| Description | Qty./Card | Cat. No. |
|--------------------------------------|-----------|----------|
| Universal Multi-Pole Breaker Lockout | 1 | 44-783 |

Single-Pole Breaker Lockout



- Unique screw clamp design works well with most single-pole breakers with trip levers up to ½” in width
- Snap on cleat accessory securely locks out long sliding switch throws with large angular rotation commonly found on some Westinghouse, ITE, Square D and Federal Pacific breakers

| Description | Qty./Card | Cat. No. |
|---------------------------------------|-----------|----------|
| Universal Single-Pole Breaker Lockout | 3 | 44-809 |
| Universal Single-Pole Breaker Lockout | 100 | 44-1809 |
| Cleat for Single-Pole Breaker Lockout | 3 | 44-785 |

Large Breaker Lockout



- Designed to lockout large 480/600V breaker switches up to 2½” wide and ¾” thick
- Easy to install — no tools required

| Description | Qty./Card | Cat. No. |
|------------------------|-----------|----------|
| Larger Breaker Lockout | 1 | 44-823 |


Single-Throw/Multi-Pole Breaker Lockout



- 480/600V lockout device designed primarily for Square D single-throw/multi-pole circuit breaker switches and most other breakers with trip levers up to 1½” wide
- Snap-on cleat accessory securely locks out long sliding switch throws with large angular rotation commonly found on some Westinghouse, ITE, Square D and Federal Pacific breakers

| Description | Qty./Card | Cat. No. |
|---|-----------|----------|
| Single-Throw/Multi-Pole Breaker Lockout | 1 | 44-807 |
| Single-Throw/Multi-Pole Breaker Lockout | 100 | 44-1807 |
| Cleat for Single-Throw/Multi-Pole Lockout | 1 | 44-786 |

Oversized Circuit Breaker Lockout System



To comply with:
 “The provisions for locking or adding a lock to the disconnecting means shall be permanently installed on or at the switch or circuit breaker used as the disconnecting means.”
Article 430.102(B) Motor 2002 NEC.

- Unique Lockout system for oversized 480/600V Circuit Breakers up to 6 inches wide.
- System can be permanently installed into an electrical panel putting all lockout items at the point of need
- Pegs in mounting rails mate with holes in locking arms for security of arm when lock is in place
- Red arms lock off, green arms lock on

| Description | Qty./Card | Cat. No. |
|---|-----------|----------|
| Oversized Circuit Breaker System - 480-600 Volt | 1 | 44-822 |

MISC ELECTRICAL: FLUID POWER


Wall Switch Lockouts



- Our patent pending universal Wall Switch Lockout locks out both toggle and decora wall switches
- The universal design assures switch is locked on or off. It also hinges open for unobstructed normal switch operation
- The standard wall switch lockout fits most wall-mounted single or three-way electrical switches

| Description | Qty./Card | Cat. No. |
|--|-----------|----------|
| Universal Wall Switch Lockout | 1 | 44-772 |
| Standard Wall Switch Lockout (not shown) | 1 | 44-789 |

Ball Valve Lockout Devices



- Best available method for locking out ball valves
- Patented design fits most major brand ball valves
- Designed to lock in off position only
- Complies with OSHA lockout standard

| Valve Size (In.) | Max. Shackle Length | Material | Cat. No. |
|---------------------|---------------------|---------------|----------|
| ½ to 1¼ | — | Polypropylene | 44-846 |
| 1¼ to 3 | — | Polypropylene | 44-847 |
| 1¼ to 1 (not shown) | ½ | Nylon | 44-820 |
| 1¼ to 3 (not shown) | ½ | Heavy Steel | 44-821 |

Circuit Breaker Lockout System

- Covers most 120V - 227V breakers!
- Works on a wide range of breakers, including single- and multi-pole configurations
- Allows panel door to be closed even when lockouts are in place
- Accommodates multiple locks, facilitating group lockout activity without hasps
- Keeps weight off the breakers, protecting delicate electrical components from damage



| Description | Qty./Card | Cat. No. |
|--|-----------|----------|
| Snap-on lockout for Square D NQO and other breakers with a hole in the switch | 1 | 44-768 |
| Clamp-on lockout for breakers without hole in switch tongue, including multi-pole breakers with tie bars | 1 | 44-764 |
| 4 in. Lock Rail with seven lock loops | 1 | 44-769 |
| No shackle lock | 1 | 444.001 |

Adjustable Cable Lockout

- Infinitely adjustable safety hasp and cable
- Ideal for multiple circuit breaker panels and side-by-side gate valve lockouts
- Feed the cable end through the points to be locked out, then back through the lockout body. Cinch it tight to remove any slack with the patented locking feature
- Tough, flexible multi-stranded 6 ft. ¼" dia. steel cable is insulated with a clear vinyl coating
- Tough, lightweight, dielectric Xenoy® thermoplastic body withstands chemicals; performs effectively in extreme conditions
- Up to four workers can apply their personal safety locks
- Complete with high-visibility, re-usable, write-on safety labels (English, French and Spanish). Identify the responsible person, then erase for the next job.



| Description | Cat. No. |
|--------------------------|----------|
| Adjustable Cable Lockout | 44-808 |

Plug Lockouts



- Accommodate a variety of electrical plug and cord sizes to prevent accidental connection or disconnection
- Durable plastic body resists wear, chemicals and job-site abuse
- Accommodates cable ties or padlocks (with up to ¾ in. shackles)

| Description | Size | Cat. No. |
|--------------------------|----------------|----------|
| Plug Lockouts – 110V | 2" × 2" × ¾" | 44-818 |
| Plug Lockouts – 220/550V | 3¼" × 3¼" × 7" | 44-819 |

Gate Valve Lockouts



- Unique patent pending rotating design allows for easier installation in confined space applications
- Each size rotates into itself and nests within the next larger size to save space in storage
- Up to four workers can apply their personal safety locks
- Complete with high-visibility permanent safety labels (English, French & Spanish) that can be written on to identify the responsible person, then erased for the next job
- Tough, lightweight, dielectric Xenoy thermoplastic bodies withstand chemicals; perform effectively in extreme conditions (temperature range -50°F (-46°C) to +350°F (177°C))

| Valve Size | Qty./Pkg. | Cat. No. |
|-------------------------------|-----------|----------|
| 1" to 3" | 1 | 44-824 |
| 2" to 5" | 1 | 44-825 |
| Set of five sizes (1" to 13") | 1 | 44-817 |

TAGS, LOCKS, AND ACCESSORIES

Flash Protection Labels and Signs

National Electric Code 110.16 Flash Protection: Switchboards, panel boards, industrial control panels, and motor control centers, in other than dwelling occupancies, that are likely to require examination, adjustment, servicing or maintenance while energized, shall be field marked to warn qualified persons of potential electric arc flash hazards. The marking shall be located so as to be clearly visible to qualified persons before examination, adjustment, servicing or maintenance of the equipment.

**Required Labels –
44-892/44-893**



**Arc Flash Labels
44-894/44-895**



**Recommended Signs –
44-896**



| Description | Type | Size | Qty./Bag | Cat. No. |
|------------------------|-------------------------|----------|----------|---------------|
| NEC Arc Flash, Warning | Self-Sticking Polyester | 3½" × 5" | 5 | 44-892 |
| NEC Arc Flash, Warning | Self-Sticking Polyester | 5" × 7" | 5 | 44-893 |
| NEC Arc Flash, Danger | Self-Sticking Polyester | 5" × 7" | 5 | 44-894 |
| NEC Arc Flash, Danger | Self-Sticking Polyester | 4" × 6" | 5 | 44-895 |
| NEC Arc Flash, Warning | Self-Sticking Polyester | 7" × 10" | 1 | 44-896 |

Lockout Tags



- High-visibility lettering
- Laminated plastic tags have non-fade legends, resist corrosive and harsh environmental conditions and a 3/8" grommet
- Polyester tags are silk screened with a metal grommet; red tie fastener included
- Exceeds OSHA's 50-lb. pullout requirement

| Legend | Type | Qty. | Cat. No. |
|--|----------------------|------------|----------------|
| Do Not Operate | Heavy-Duty Laminated | Card of 5 | 44-830 |
| Do Not Operate | Heavy-Duty Laminated | Box of 100 | 44-1830 |
| Do Not Operate | Polyester | Bag of 25 | 44-848 |
| Do Not Operate – Maintenance Department | Heavy-Duty Laminated | Card of 5 | 44-831 |
| Do Not Operate – Maintenance Department | Polyester | Bag of 25 | 44-844 |
| Do Not Operate – Electricians at Work | Heavy-Duty Laminated | Card of 5 | 44-832 |
| Do Not Operate – Electricians at Work | Polyester | Bag of 25 | 44-843 |
| Do Not Operate – (red striped background) | Heavy-Duty Laminated | Card of 5 | 44-833 |
| Do Not Operate – (red striped background) | Heavy-Duty Laminated | Box of 100 | 44-1833 |
| Do Not Operate – (red striped background) | Polyester | Bag of 25 | 44-849 |
| Do Not Operate – Lockout Steps Required | Heavy-Duty Laminated | Card of 5 | 44-835 |
| Do Not Operate – (Photo ID - Self Sealant) | Heavy-Duty Laminated | Card of 5 | 44-834 |

Xenoy Safety Lockout Padlocks



- Dedicated safety lockout device reduces confusion with other locks
- Non-conductive, lightweight Xenoy® body
- 1½" shackle clearance
- 1½" wide lock with 3/8" shackle
- Four colors for easy identification
- Keyed alike and Master-Keyed locks available by special order

| Bumper Color | Cat. No. |
|--------------|---------------|
| Blue | 44-912 |
| Black | 44-914 |
| Red | 44-916 |
| Yellow | 44-918 |

Steel Padlocks



- Rustproofed, steel case with nickel-plated shackle withstands abuse and environmental hazards
- Includes two keys
- 1½" wide lock with 3/8" shackle diameter
- Keyed-alike and Master-Keyed locks available by special order

| Bumper Color | 3/8" Shackle Clearance Cat. No. | 2" Shackle Clearance Cat. No. |
|--------------|---------------------------------|-------------------------------|
| Blue | 44-900 | 44-901 |
| Black | 44-902 | 44-903 |
| White | 44-904 | 44-905 |
| Red | 44-906 | 44-907 |
| Green | 44-908 | 44-909 |
| Yellow | 44-910 | 44-911 |

Lock Labels



- Easy identification of employees' locks
- Write-on, vinyl labels with peel-off adhesive backing
- Polyester over laminate protects label

| Description | Cat. No. |
|-------------|---------------|
| Lock Labels | 44-898 |

Safety Lockout Hasps



- Allow up to six workers to lock out a single energy source
- Rustproofed, plated and vinyl-coated
- Labeled hasps feature anodized aluminum alloy construction for long-term durability
- Permanent "Do Not Operate" labels accept pens, pencils and permanent markers

Safety Lockout Hasps

| Jaw Diameter | Qty./Card | Cat. No. |
|--------------|-----------|---------------|
| 1" | 3 | 44-800 |
| 1½" | 2 | 44-801 |

Labeled Safety Lockout Hasps

| Legend | Color | Qty./Card | Cat. No. |
|----------------|-------|-----------|---------------|
| Do Not Operate | Blue | 1 | 44-790 |
| Do Not Operate | Red | 1 | 44-791 |

KITS: STATIONS

Standard Lockout/Tagout Kit

- Excellent selection of lockout/tagout devices, tags and locks for maintenance workers or contractors
- Small nylon zipper pouch features belt loops and d-rings for easy attachment to belts, tool pouches, tool carts and more



| Description | | Cat. No. |
|--|-------------|-----------------|
| Standard Lockout/Tagout Kit | | 44-971 |
| Kit 44-971 Includes: | Qty. | Cat. No. |
| Hinged Single-Pole Breaker Lockout | 3 | 44-810 |
| Universal 277V Breaker Lockout/Single Pole | 2 | 44-809 |
| 480/600V Breaker Lockout | 1 | 44-807 |
| Wall Switch Lockout | 1 | 44-789 |
| 110V Small Plug Lockout | 1 | 44-818 |
| 2 in. Shackle Red Padlocks | 2 | 44-907 |
| 1 in. Safety Lockout Hasps | 2 | 44-800 |
| Lockout Tags – Do Not Operate | 5 | 44-830 |
| Lockout Tags – Do Not Operate (striped) | 5 | 44-833 |
| Cleat for 277V Breaker Lockout | 1 | 44-785 |
| Cleat for 480/600V Breaker Lockout | 1 | 44-786 |
| Universal Multi-Pole Breaker Lockout | 2 | 44-783 |
| Zipper Pouch | 1 | IA-3240 |

Quantities listed in kit description are for individual pieces, not carded packages.

Basic Lockout/Tagout Kit

- A great selection of the most popular lockout/tagout devices
- Small nylon zipper pouch features belt loops and d-rings for easy attachment to belts, tool pouches, tool carts and more



| Description | | Cat. No. |
|--|-------------|-----------------|
| Basic Lockout/Tagout Kit | | 44-970 |
| Kit 44-970 Includes: | Qty. | Cat. No. |
| Hinged Single-Pole Breaker Lockout | 2 | 44-810 |
| Universal 277V Breaker Lockout/Single Pole | 1 | 44-809 |
| 480/600V Breaker Lockout | 1 | 44-807 |
| Wall Switch Lockout | 1 | 44-789 |
| 3/4 in. Red Padlock | 1 | 44-906 |
| 1 in. Safety Lockout Hasp | 1 | 44-800 |
| Lockout Tags – Do Not Operate (striped) | 5 | 44-833 |
| Universal Multi-Pole Breaker Lockout | 1 | 44-783 |
| 110V Plug Lockout | 1 | 44-818 |
| Zipper Pouch | 1 | IA-3240 |

Quantities listed in kit description are for individual pieces, not carded packages.

Industrial Lockout/Tagout Kit

- An industrial selection of lockout/tagout devices
- Polypropylene plastic tool box resists oil and chemicals



| Description | | Cat. No. |
|---|-------------|-----------------|
| Industrial Lockout/Tagout Kit | | 44-974 |
| Kit 44-974 Includes: | Qty. | Cat. No. |
| Hinged Single-Pole Breaker Lockout | 3 | 44-810 |
| Universal Breaker/Single Pole Lockout | 2 | 44-809 |
| 480/600V Breaker Lockout | 1 | 44-807 |
| Wall Switch Lockout | 1 | 44-789 |
| 110V Small Plug Lockout | 1 | 44-818 |
| Ball Valve Lockout | 1 | 44-820 |
| 1 in. Safety Lockout Hasp | 2 | 44-800 |
| Red Labeled Lockout | 1 | 44-791 |
| 220/550V Plug Lockout | 1 | 44-819 |
| Lockout Tags – Do Not Operate (striped) | 10 | 44-849 |
| Fuse Blockout | 1 | 44-815 |
| Fuse Blockout | 1 | 44-816 |
| Gate Valve Lockout | 1 | 44-824 |
| Cleat for Breaker Lockout #44-809 | 1 | 44-785 |
| Cleat for 480/600V Breaker Lockout | 1 | 44-786 |
| Red Lockout Padlocks | 4 | 44-916 |
| Universal Multi-Pole Breaker Lockout | 2 | 44-783 |
| Tool Box | 1 | IA-3241 |

Quantities listed in kit description are for individual pieces, not carded packages.

Lock Stations

- Integrated, one-piece molded construction eliminates loose parts
- Polycarbonate material provides twice the heat resistance and quadruple the impact strength of typical stations
- Reinforced snap-lock clips provide easy padlock and hasp storage and removal
- Exclusive translucent cover protects contents
 - Lockable to prevent loss of valuable safety lockout padlocks. Recommend using a combination lock for simple access control
 - Innovative hinge holds cover open for easy product selection



| Description | Cat. No. |
|--|---------------|
| Four-Lock Station (board only) | 44-777 |
| Four-Lock Station Kit includes four red safety Padlocks (44-916), 12 Heavy-Duty Lockout Tags and two 1 in. Safety Lockout Hasps (44-800) | 44-778 |
| Ten-Lock Station (board only) | 44-805 |
| Ten-Lock Station Kit includes ten red safety Padlocks (44-916), 24 Heavy-Duty Lockout Tags and two 1 in. Safety Lockout Hasps (44-800) | 44-806 |

IDEAL INDUSTRIES, INC.

Becker Place, Sycamore, IL 60178, USA / 815-895-5181 • 800-435-0705 in USA

International offices:

Australia • Brazil • Canada • China • Germany • India • Mexico • UK

For complete sales office contact information, visit us at:

www.idealind.com