



**LED QUICK
REFERENCE
GUIDE
JUNE 2016**

LED SPECIALTY LAMPS

LED filament lamps

Applications / Features

- LED with a traditional incandescent look and feel
- Omni-directional light source
- Smooth dimming
- Replaces up to 60 watt lamps
- Long life - 15,000 hours
- Damp location
- Approved for totally enclosed fixtures
- cUL listed



LED Filament Lamps



Item Number	Lamp Description	W	Bulb Type	Base	V	Finish	CCT	Lm	CRI	M.O.L. (Inches)	Life/ Hrs.	UPC	Pack
S9560	4.5A15/CL/LED/E26/27K/120V	4.5	A15	E26	120	Clear	2700K	450	80	3 3/8	15K	045923095603	24/6
S9561	4.5A19/CL/LED/E26/27K/120V	4.5	A19	E26	120	Clear	2700K	450	80	4 1/8	15K	045923095610	24/6
S9562	6.5A19/CL/LED/E26/27K/120V	6.5	A19	E26	120	Clear	2700K	810	80	4 1/8	15K	045923095627	24/6
S9563*	4.5G25/CL/LED/E26/27K/120V	4.5	G25	E26	120	Clear	2700K	450	80	4 3/8	25K	045923095634	24/6
S9564	6.5G25/CL/LED/E26/27K/120V	6.5	G25	E26	120	Clear	2700K	810	80	4 3/8	15K	045923095641	24/6
S9565	4.5G40/CL/LED/E26/27K/120V	4.5	G40	E26	120	Clear	2700K	450	80	6 1/2	15K	045923095658	24/6
S9566	6.5G40/CL/LED/E26/27K/120V	6.5	G40	E26	120	Clear	2700K	810	80	6 1/2	15K	045923095665	24/6
S9820+	2W CTC/LED/27K/CL/120V/AG	2	C35	E12	120	Clear	2700K	190	80	3 7/8	15K	045923098208	24/6
S9821+	2W CFC/LED/27K/CL/120V/AG	2	CA35	E12	120	Clear	2700K	190	80	4 11/16	15K	045923098215	24/6
S9822+	4W CTC/LED/27K/CL/120V/AG	4	C35	E12	120	Clear	2700K	340	80	3 7/8	15K	045923098222	24/6
S9823+	4W CFC/LED/27K/CL/120V/AG	4	CA35	E12	120	Clear	2700K	340	80	4 11/16	15K	045923098239	24/6
S9567*	2.5W ETC/LED/27K/120V	2.5	C35	E26	120	Clear	2700K	250	80	3 1/2	15K	045923095672	24/6
S9568*	2.5W CTC/LED/27K/120V	2.5	C35	E12	120	Clear	2700K	250	80	4 5/16	15K	045923095689	24/6
S9569*	4.5W ETC/LED/27K/120V	4.5	C35	E26	120	Clear	2700K	450	80	3 1/2	15K	045923095696	24/6
S9570*	4.5W CTC/LED/27K/120V	4.5	C35	E12	120	Clear	2700K	450	80	4 5/16	15K	045923095702	24/6
S9571	2.5W EFC/LED/27K/120V	2.5	CA35	E26	120	Clear	2700K	250	80	4 5/16	15K	045923095719	24/6
S9572	2.5W CFC/LED/27K/120V	2.5	CA35	E12	120	Clear	2700K	250	80	5	15K	045923095726	24/6
S9573	4.5W EFC/LED/27K/120V	4.5	CA35	E26	120	Clear	2700K	450	80	4 5/16	15K	045923095733	24/6
S9574	4.5W CFC/LED/27K/120V	4.5	CA35	E12	120	Clear	2700K	450	80	5	15K	045923095740	24/6
S9575	4.5BT15/CL/LED/E26/27K/120V	4.5	BT15	E26	120	Clear	2700K	450	80	4 1/8	15K	045923095757	24/6
S9576	6.5BT15/CL/LED/E26/27K/120V	6.5	BT15	E26	120	Clear	2700K	810	80	4 1/8	15K	045923095764	24/6
S9581	6.5ST19/CL/LED/E26/27K/120V	6.5	ST19	E26	120	Clear	2700K	810	80	5 1/2	15K	045923095818	24/6
S9582	6.5T9/CL/LED/E26/27K/120V	6.5	T9	E26	120	Clear	2700K	800	80	12	15K	045923095825	24/6
S9580	4.5T10/LED/E26/27K/120V	4.5	T10	E26	120	Clear	2700K	430	80	5	15K	045923095801	24/6

*AG - All glass envelope

Vintage Style LED filament lamps

Applications / Features

- LED with a traditional vintage look and feel
- Amber finish
- Omni-directional light source
- Smooth dimming
- 2200 & 2300K - warm tone color temperature
- Replaces up to 60 watt lamps
- Long life - 15,000 hours
- Damp location
- Approved for totally enclosed fixtures
- cUL listed



S9577,
S9578, S9579
ST19



S9584
G25
NEW



S9583
A19
NEW



S9588
T9
NEW



S9585
ST19
NEW



S9586
C35
NEW



S9587
CA35
NEW

LED Filament Lamps



Item Number	Lamp Description	W	Bulb Type	Base	V	Finish	CCT	Lm	CRI	M.O.L. (Inches)	Life/Hrs.	UPC	Pack
S9577	2.5ST19/AMB/LED/E26/23K/120V	2.5	ST19	E26	120	Amber	2300K	220	80	5 3/8	15K	045923095771	24/6
S9578	4.5ST19/AMB/LED/E26/23K/120V	4.5	ST19	E26	120	Amber	2300K	400	80	5 3/8	15K	045923095788	24/6
S9579	6.5ST19/AMB/LED/E26/23K/120V	6.5	ST19	E26	120	Amber	2300K	650	80	5 3/8	15K	045923095795	24/6
S9583	4.5A19/AMB/LED/E26/22K/120V	4.5	A19	E26	120	Amber	2200K	380	80	4 1/8	15K	045923095832	24/6
S9584	4.5G25/AMB/LED/E26/22K/120V	4.5	G25	E26	120	Amber	2200K	380	80	4 3/8	15K	045923095849	24/6
S9585	4.5ST19/AMB/LED/E26/22K/120V	4.5	ST19	E26	120	Amber	2200K	380	80	5 1/2	15K	045923095856	24/6
S9586	4CTA/LED/AMB/22K/120V	4	C35	E12	120	Amber	2200K	300	80	4 5/16	15K	045923095863	24/6
S9587	4CFA/LED/AMB/22K/120V	4	CA35	E12	120	Amber	2200K	300	80	5	15K	045923095870	24/6
S9588	6.5T9/AMB/LED/E26/22K/120V	6.5	T9	E26	120	Amber	2200K	620	80	12	15K	045923095887	24/6


OMNI-DIRECTIONAL LED A19 LAMPS

40 & 60W replacement omni-directional LED A19 lamps

Direct replacements for 40 Watt & 60 Watt incandescent lamps

Applications / Features

- Direct replacement for 40—60 Watt incandescent lamps uses only 5.5—9 Watts
- Indoor residential and commercial lighting
- Damp location
- Approved for totally enclosed fixtures
- Accent lighting
- Dimmable



Omni 300° LED A19 Lamps



Item Number	Lamp Description	W	V	CRI	CCT	Lm	Bm	M.O.L. (Inches)	Life/Hrs.	UPC	Pack
S9600*	5.5A19/OMNI/300/LED/27K	5.5	120	80	2700K	450	300°	4 5/16	25K	045923096006	24/6
S9601*	5.5A19/OMNI/300/LED/30K	5.5	120	80	3000K	470	300°	4 5/16	25K	045923096013	24/6
S9602*	5.5A19/OMNI/300/LED/35K	5.5	120	80	3500K	480	300°	4 5/16	25K	045923096020	24/6
S9603*	5.5A19/OMNI/300/LED/40K	5.5	120	80	4000K	490	300°	4 5/16	25K	045923096037	24/6
S9604*	5.5A19/OMNI/300/LED/50K	5.5	120	80	5000K	510	300°	4 5/16	25K	045923096044	24/6
S9605*	9A19/OMNI/300/LED/27K	9	120	80	2700K	800	300°	4 5/16	25K	045923096051	24/6
S9606*	9A19/OMNI/300/LED/30K	9	120	80	3000K	830	300°	4 5/16	25K	045923096068	24/6
S9607*	9A19/OMNI/300/LED/35K	9	120	80	3500K	845	300°	4 5/16	25K	045923096075	24/6
S9608*	9A19/OMNI/300/LED/40K	9	120	80	4000K	860	300°	4 5/16	25K	045923096082	24/6
S9609*	9A19/OMNI/300/LED/50K	9	120	80	5000K	900	300°	4 5/16	25K	045923096099	24/6
S9610*	9A19/OMNI/300/LED/27K/GU24	9	120	80	2700K	800	300°	4 5/16	25K	045923096105	24/6
S9611*	9A19/OMNI/300/LED/35K/GU24	9	120	80	3500K	845	300°	4 5/16	25K	045923096112	24/6
90 CRI											
S9612*	10.5A19/OMNI/LED/27K/90CRI	10.5	120	90	2700K	800	300°	4 5/8	25K	045923096129	24/6
S9613*	10.5A19/OMNI/LED/27K/90CRI/GU24	10.5	120	90	2700K	800	300°	4 1/2	25K	045923096136	24/6
S9617*	10.5A19/OMNI/LED/30K/90CRI	10.5	120	90	3000K	830	300°	4 5/8	25K	045923096174	24/6

60W replacement omni-directional LED A19 display pack

Direct replacements for
60 Watt incandescent lamps,
uses only 9 Watts

Applications / Features

- 60W replacement uses only 9 Watts
- Indoor residential and commercial lighting
- Warm white 2700K
- Dimmable
- Damp location
- Approved for totally enclosed fixtures



9 Watt Omni 300° LED A19 Display Packs

Item Number	Lamp Description	W	V	CRI	CCT	Lm	Bm	M.O.L. (Inches)	Life/Hrs.	UPC	Pack/Master
S9378*	9A19/LED/2700K/800L/120V/D	9	120	80	2700K	800	300°	4 3/8	25K	045923093784	72



Must be ordered in full cases only.

40W replacement omni-directional LED A19 2-pack

Direct replacements for 40 Watt
incandescent lamps, uses only 6.5 Watts

Applications / Features

- 40W replacement uses only 6.5 Watts
- Indoor residential and commercial lighting
- Down lighting
- Display lighting
- Accent lighting
- 2 Lamp value pack
- Dimmable
- 2700K
- Damp location
- Approved for enclosed fixtures



6.5 Watt Omni 300° LED A19 Lamp 2-pack

Item Number	Lamp Description	W	V	CRI	CCT	Lm	Bm	M.O.L. (Inches)	Life/Hrs.	UPC	Pack/Master
S9374*	6.5A19/LED/27K/450L/120V/2PK	6.5	120	80	2700K	450	300°	4 3/16	25K	045923093746	16-2pks



Must be ordered in full cases only.


MULTI-DIRECTIONAL LED A19 LAMPS

40 & 60W replacement multi-directional LED A19 lamps

Direct replacements for 40 Watt & 60 Watt incandescent lamps

Applications / Features

- Indoor residential and commercial lighting
- Down lighting
- Display lighting
- Accent lighting
- Direct replacement for 40–60 Watt incandescent lamps, uses only 5–9.5 Watts
- Innovative design—smooth heat sink design to resemble traditional incandescent lamp
- Dimmable
- 2700K, 3000K, 3500K, 4000K and 5000K options
- Damp location
- Long life, 25,000 hours
- Approved for totally enclosed fixtures
- No UV or IR radiation
- 3 year warranty



Available July 2016

Multi-Directional A19 LED Lamps



Item Number	Lamp Description	W	V	CRI	CCT	Lm	Bm	M.O.L. (Inches)	Life/Hrs.	UPC	Pack/Master
S9830*	5A19/OMNI/220/LED/27K	5	120	80	2700K	450	220°	4 3/16	25K	045923098307	24/6
S9831*	5A19/OMNI/220/LED/30K	5	120	80	3000K	470	220°	4 3/16	25K	045923098314	24/6
S9832*	5A19/OMNI/220/LED/35K	5	120	80	3500K	480	220°	4 3/16	25K	045923098321	24/6
S9833*	5A19/OMNI/220/LED/40K	5	120	80	4000K	490	220°	4 3/16	25K	045923098338	24/6
S9834*	5A19/OMNI/220/LED/50K	5	120	80	5000K	510	220°	4 3/16	25K	045923098345	24/6
S9835*	9.5A19/OMNI/220/LED/27K	9.5	120	80	2700K	800	220°	4 3/16	25K	045923098352	24/6
S9836*	9.5A19/OMNI/220/LED/30K	9.5	120	80	3000K	830	220°	4 3/16	25K	045923098369	24/6
S9837*	9.5A19/OMNI/220/LED/35K	9.5	120	80	3500K	845	220°	4 3/16	25K	045923098376	24/6
S9838*	9.5A19/OMNI/220/LED/40K	9.5	120	80	4000K	860	220°	4 3/16	25K	045923098383	24/6
S9839*	9.5A19/OMNI/220/LED/50K	9.5	120	80	5000K	900	220°	4 3/16	25K	045923098390	24/6
S9840*	9.5A19/OMNI/220/LED/27K/GU24	9.5	120	80	2700K	800	220°	4 3/16	25K	045923098406	24/6
S9841*	9.5A19/OMNI/220/LED/35K/GU24	9.5	120	80	3500K	845	220°	4 3/16	25K	045923098413	24/6
S9842*	9.5A19/OMNI/220/LED/40K/GU24	9.5	120	80	4000K	850	220°	4 3/16	25K	045923098420	24/6

* ENERGY STAR certified - August 2016


40 & 60W replacement multi-directional LED A19 lamps

Direct replacements for 40 Watt & 60 Watt incandescent lamps

Applications / Features

- Direct replacement for 40 – 60 Watt incandescent lamps uses only 6.5–10 Watts
- Direct replacement for 9 & 13 Watt screw-in CFLs
- Indoor residential and commercial lighting
- Down lighting
- Damp location
- Approved for totally enclosed fixtures

Non-Dimmable



Multi-directional LED A19 lamps

Item Number	Lamp Description	W	V	CRI	CCT	Lm	Bm	M.O.L. (Inches)	Life/Hrs.	UPC	Pack
S9590	6.5A19/LED/2700K/120V	6.5	120	80	2700K	450	240°	4 3/16	15K	045923095900	24/6
S9591	6.5A19/LED/3000K/120V	6.5	120	80	3000K	450	240°	4 3/16	15K	045923095917	24/6
S9592	6.5A19/LED/5000K/120V	6.5	120	80	5000K	470	240°	4 3/16	15K	045923095924	24/6
S9593	10A19/LED/2700K/120V	10	120	80	2700K	800	240°	4 9/16	15K	045923095931	24/6
S9594	10A19/LED/3000K/120V	10	120	80	3000K	800	240°	4 9/16	15K	045923095948	24/6
S9595	10A19/LED/5000K/120V	10	120	80	5000K	840	240°	4 9/16	15K	045923095955	24/6

60W replacement multi-directional LED A19 4-packs

Direct replacements for 60 Watt incandescent lamps

Applications / Features

- 60W replacement uses only 9 Watts
- Indoor residential and commercial lighting
- Down lighting
- Display lighting
- Accent lighting
- Direct replacement for 13 Watt screw-in CFLs
- Innovative design—smooth heat sink design to resemble traditional incandescent lamp
- 2700K and 5000K options
- Damp location
- Approved for enclosed fixtures
- 3 year warranty*

Non-dimmable



Multi-directional LED A19 4-packs

Item Number	Lamp Description	W	V	CRI	CCT	Lm	Bm	M.O.L. (Inches)	Life/Hrs.	UPC	Pack/Master
S9596	9A19/LED/2700K/120V/4PK	9	120	80	2700K	800	200°	4 3/16	10K	045923095962	12-4pks
S9597	9A19/LED/5000K/120V/4PK	9	120	80	5000K	800	200°	4 3/16	10K	045923095979	12-4pks

* Visit www.satco.com for details

Must be ordered in full cases only.


OMNI-DIRECTIONAL LED A19 LAMPS

75W replacement 300° omni-directional LED lamps

Direct replacement for
75 Watt incandescent lamps
uses only 12 Watts.

Applications / Features

- Indoor residential and commercial lighting
- Down lighting
- Display lighting
- Accent lighting
- Dimmable
- Damp Location
- Approved for totally enclosed fixtures



300° Omni-Directional LED Lamps


Item Number	Lamp Description	W	V	CRI	CCT	Lm	Bm	M.O.L. (Inches)	Life/ Hrs.	UPC	Pack
S9241*	12A19/LED/2700K/1100L/120V/D	12	120	80	2700K	1100	300°	4 5/8	25K	045923092411	24/6
S9242*	12A19/LED/3000K/1140L/120V/D	12	120	80	3000K	1140	300°	4 5/8	25K	045923092428	24/6
S9243	12A19/LED/4000K/1190L/120V/D	12	120	80	4000K	1190	300°	4 5/8	25K	045923092435	24/6
S9244	12A19/LED/5000K/1230L/120V/D	12	120	80	5000K	1230	300°	4 5/8	25K	045923092442	24/6
S9238*	12A19/LED/2700K/1100L/120V/D/GU24	12	120	80	2700K	1100	300°	4 5/8	25K	045923092381	24/6

75W replacement 220° omni-directional LED lamps

Direct replacement for
75 Watt incandescent lamps
uses only 11.5 Watts.

Applications / Features

- Indoor residential and commercial lighting
- Down lighting
- Display lighting
- Accent lighting
- Dimmable
- Damp Location
- Approved for totally enclosed fixtures



Available July 2016



220° Omni-Directional LED Lamps

Item Number	Lamp Description	W	V	CRI	CCT	Lm	Bm	M.O.L. (Inches)	Life/ Hrs.	UPC	Pack
S9810*	11.5A19/LED/2700K/1100L/120V/D	11.5	120	80	2700K	1100	220°	4 5/8	25K	045923098109	24/6
S9811*	11.5A19/LED/3000K/1140L/120V/D	11.5	120	80	3000K	1140	220°	4 5/8	25K	045923098116	24/6
S9812*	11.5A19/LED/4000K/1190L/120V/D	11.5	120	80	4000K	1190	220°	4 5/8	25K	045923098123	24/6
S9813*	11.5A19/LED/5000K/1230L/120V/D	11.5	120	80	5000K	1230	220°	4 5/8	25K	045923098130	24/6
S9814*	11.5A19/LED/2700K/1100L/120V/D/GU24	11.5	120	80	2700K	1100	220°	4 1/2	25K	045923098147	24/6

* ENERGY STAR certified - August 2016


OMNI-DIRECTIONAL LED A19 & A21 LAMPS

100W replacement omni-directional LED lamps

Direct replacement for 100 Watt incandescent lamps uses only 16 Watts

Applications/Features

- Indoor residential and commercial lighting
- Down lighting
- Display lighting
- Accent lighting
- Damp location
- Approved for totally enclosed fixtures



Omni-Directional LED Lamps

Item Number	Lamp Description	W	V	CRI	CCT	Lm	Bm	M.O.L. (Inches)	Life/Hrs.	UPC	Pack
S9284*	16A21/LED/2700K/1600L/120V/D	16	120	80	2700K	1600	300°	5 9/16	25K	045923092848	24/6
S9285*	16A21/LED/3000K/1650L/120V/D	16	120	80	3000K	1650	300°	5 9/16	25K	045923092855	24/6
S9286	16A21/LED/4000K/1720L/120V/D	16	120	80	4000K	1720	300°	5 9/16	25K	045923092862	24/6
S9287	16A21/LED/5000K/1800L/120V/D	16	120	80	5000K	1800	300°	5 9/16	25K	045923092879	24/6
S9288*	16A21/LED/2700K/1600L/120V/D/GU24	16	120	80	2700K	1600	300°	5 9/16	25K	045923092886	24/6

75W & 100W replacement LED 4 packs

Direct replacement for 75 Watt & 100 Watt incandescent lamps

Applications / Features


- Indoor residential and commercial lighting
- Down lighting
- Display lighting
- Accent lighting
- Convenient 4 packs
- Direct replacement for 75 Watt & 100 Watt incandescent lamps uses only 11 Watts & 15 Watts
- Innovative design — smooth heat sink design to resemble traditional incandescent lamp
- 240° Multi-directional
- 2700K and 5000K options
- Damp location rated
- Long life, 15,000 hours
- Approved for totally enclosed fixtures
- High efficiency/environmentally friendly
- No UV or IR radiation
- 3 year warranty



S9800, S9801

S9802, S9803

Available July 2016



Omni-Directional LED Lamps

Item Number	Lamp Description	W	V	CRI	CCT	Lm	Bm	M.O.L. (Inches)	Life/Hrs.	UPC	Pack (4-pks)
S9800	11A19/LED/2700K/120V/4PK	11	120	80	2700K	1100	240°	4 9/16	15K	045923098000	12/4
S9801	11A19/LED/5000K/120V/4PK	11	120	80	5000K	1150	240°	4 9/16	15K	045923098017	12/4
S9802	15A21/LED/2700K/120V/4PK	15	120	80	2700K	1500	240°	5 1/4	15K	045923098024	12/4
S9803	15A21/LED/5000K/120V/4PK	15	120	80	5000K	1570	240°	5 1/4	15K	045923098031	12/4


OMNI-DIRECTIONAL LED A19 & A21 LAMPS

30, 70 & 100 Watt replacement omni-directional 3-Way LED lamps

Direct replacement for 30/70/100W
3-way incandescent lamps
uses only 3/11/16 Watts

Applications / Features

- Indoor residential and commercial lighting
- Down lighting
- Display lighting
- Accent lighting
- Damp location rated
- Approved for totally enclosed fixtures




Omni-Directional LED Lamps

Item Number	Lamp Description	W	V	CRI	CCT	Lumens	Bm	M.O.L. (Inches)	Life/Hrs.	UPC	Pack
S9370*	3/11/16A21/3-WAY LED/2700K/120V	3/11/16	120	80	2700K	350/1200/1600	300°	5 9/16	25K	045923093708	24/6
S9371*	3/11/16A21/3-WAY LED/3000K/120V	3/11/16	120	80	3000K	360/1240/1650	300°	5 9/16	25K	045923093715	24/6
S9372	3/11/16A21/3-WAY LED/4000K/120V	3/11/16	120	80	4000K	375/1290/1720	300°	5 9/16	25K	045923093722	24/6
S9373	3/11/16A21/3-WAY LED/5000K/120V	3/11/16	120	80	5000K	390/1350/1800	300°	5 9/16	25K	045923093739	24/6

KolourOne Omni^X 10.5W A19 360° omni-directional LED lamps

Applications / Features

- Direct replacement for 60W A19 uses only 10.5 Watts
- Indoor residential and commercial lighting
- Down lighting
- Display lighting
- Table lamps
- Pendants
- Dimmable



KolourOne Omni^X 10.5W A19 Omni-Directional LED Lamps

Item Number	Lamp Description	W	V	CRI	CCT	Lm	Bm	M.O.L. (Inches)	Life/Hrs.	UPC	Pack
S9037*	10.5A19/OMNI/LED/2700K	10.5	120	84	2700K	810	360°	4 1/2	25K	045923090370	24/6
S9039	10.5A19/OMNI/LED/5000K	10.5	120	83	5000K	870	360°	4 1/2	25K	045923090394	24/6

LED REFLECTOR LAMPS

Dimension™ warm tone dimming LED lamps

Applications/Features

- Indoor residential and commercial lighting
- Down lighting
- Display lighting
- Accent lighting
- Dims from 2700K to 2200K

Dimension Warm Tone Dimming lamps feature an on-board "Direct Drive" integrated circuit with a microprocessor chip. This "Smart" chip manages the path of current which changes the CCT from 2700K down to 2200K.

This new generation of LED lamp technology has been tested with a wide assortment of dimmers and this list (shown left) reflects the ones we have selected to deliver the best overall dimming experience, while reaching the lowest dim level and lowest possible color temperature.



S9073
R20





S9025
R30



S9101
R40

RECOMMENDED DIMMERS	
Manufacturer	Model No.
Lutron	SLV600P MAGNETIC LOW VOLTAGE
Lutron	CT-603PGH ECO DIM INCANDESCENT
Lutron	DV600PR DIVA INCANDESCENT
Leviton	6674 UNIVERSAL LED
Cooper	DLC03P LED
Maximum number of lamps per dimmer = 10	

Dims to warmer color like an incandescent



Dimension Warm Tone Dimming LED Lamps

Item Number	Lamp Description	W	V	CRI	CCT	Lm	Bm	M.O.L. (Inches)	Life/Hrs.	UPC	Pack
S9073*	7.8R20/LED/2700K	7.8	120	80	2700K	460	108°	3 7/8	30K	045923090738	24/6
S9025*	12.8R30/LED/2700K	12.8	120	80	2700K	750	108°	5 1/4	40K	045923090257	12/1
S9101*	16R40/LED/2700K	16	120	80	2700K	1000	108°	6 3/8	30K	045923092015	12/1

Consult Satco or visit www.satco.com for an up to date dimmer compatibility list.




LED REFLECTOR LAMPS

Satco 6.5W R20 LED reflectors 80 & 90 CRI

Applications / Features

- 50R20 replacement uses only 6.5 Watts
- Indoor residential and commercial lighting
- Down lighting
- Display lighting
- Dimmable**
- Damp location



6.5W R20 LED Reflectors

Item Number	Lamp Description	W	V	CRI	CCT	Lm	Bulb Type	M.O.L. (Inches)	Life/ Hrs.	UPC	Pack
S9630*	6.5R20/LED/2700K/525L/120V	6.5	120	80	2700K	525	R20	3 15/16	25K	045923096303	24/6
S9631*	6.5R20/LED/3000K/540L/120V	6.5	120	80	3000K	540	R20	3 15/16	25K	045923096310	24/6
S9632*	6.5R20/LED/4000K/560L/120V	6.5	120	80	4000K	560	R20	3 15/16	25K	045923096327	24/6
S9633*	6.5R20/LED/5000K/580L/120V	6.5	120	80	5000K	580	R20	3 15/16	25K	045923096334	24/6

90 CRI


S9614	6.5R20/LED/2700K/450L/90CRI	6.5	120	90	2700K	450	R20	3 15/16	25K	045923096143	24/6
-------	-----------------------------	-----	-----	----	-------	-----	-----	---------	-----	--------------	------

** Consult Satco or visit www.satco.com for an up to date dimmer compatibility list.

Satco 9.5W BR30 LED reflectors 80 & 90 CRI

Applications / Features

- 65BR30 replacement uses only 9.5 Watts
- Indoor residential and commercial lighting
- Down lighting
- Display lighting
- New one piece, lighter weight design
- Dimmable**
- Damp location



9.5W BR30 LED Reflectors

Item Number	Lamp Description	W	V	CRI	CCT	Lm	Bulb Type	M.O.L. (Inches)	Life/ Hrs.	UPC	Pack
S9620*	9.5BR30/LED/2700K/750L/120V/D	9.5	120	80	2700K	750	BR30	5 3/16	25K	045923096204	12/6
S9621*	9.5BR30/LED/3000K/800L/120V/D	9.5	120	80	3000K	800	BR30	5 3/16	25K	045923096211	12/6
S9622*	9.5BR30/LED/4000K/830L/120V/D	9.5	120	80	4000K	830	BR30	5 3/16	25K	045923096228	12/6
S9623*	9.5BR30/LED/5000K/860L/120V/D	9.5	120	80	5000K	860	BR30	5 3/16	25K	045923096235	12/6
S9624*	9.5BR30/LED/2700K/GU24/750L/120V	9.5	120	80	2700K	750	BR30	4 15/16	25K	045923096242	12/6

90 CRI

S9625*	9.5BR30/LED/2700K/670L/120V/D	9.5	120	90	2700K	650	BR30	5 3/16	25K	045923096259	12/6
S9626*	9.5BR30/LED/2700K/GU24/670L/120V	9.5	120	90	2700K	650	BR30	4 15/16	25K	045923096266	12/6


** Consult Satco or visit www.satco.com for an up to date dimmer compatibility list.

LED REFLECTOR LAMPS

Satco 11.5W & 16.5W BR40 LED reflectors 80 & 90 CRI

Applications / Features

- 65W BR40 replacement uses only 11.5W
- 85W BR40 replacement uses only 16.5W
- Indoor residential and commercial lighting
- Down lighting
- Display lighting
- Dimmable**
- Damp location



11.5W & 16.5W BR40 LED Reflectors



Item Number	Lamp Description	W	V	CRI	CCT	Lm	Bulb Type	M.O.L. (Inches)	Life/Hrs.	UPC	Pack
S9634*	11.5BR40/LED/2700K/940L/120V	11.5	120	80	2700K	940	BR40	6 7/16	25K	045923096341	12/6
S9635*	11.5BR40/LED/3000K/970L/120V	11.5	120	80	3000K	970	BR40	6 7/16	25K	045923096358	12/6
S9636*	11.5BR40/LED/4000K/1000L/120V	11.5	120	80	4000K	1000	BR40	6 7/16	25K	045923096365	12/6
S9637*	11.5BR40/LED/5000K/1050L/120V	11.5	120	80	5000K	1050	BR40	6 7/16	25K	045923096372	12/6
S9638*	16.5BR40/LED/2700K/1200L/120V	16.5	120	80	2700K	1200	BR40	6 7/16	25K	045923096389	12/6
S9639*	16.5BR40/LED/3000K/1230L/120V	16.5	120	80	3000K	1230	BR40	6 7/16	25K	045923096396	12/6
S9640*	16.5BR40/LED/4000K/1280L/120V	16.5	120	80	4000K	1280	BR40	6 7/16	25K	045923096402	12/6
S9641*	16.5BR40/LED/5000K/1320L/120V	16.5	120	80	5000K	1320	BR40	6 7/16	25K	045923096419	12/6
90 CRI											
S9615	16.5BR40/LED/2700K/1075L/90CRI	16.5	120	90	2700K	1075	BR40	3 7/16	25K	045923096150	12/6

** Consult Satco or visit www.satco.com for an up to date dimmer compatibility list.

Satco LED 8.5W BR30 Ditto

Applications / Features

- 65W BR30 replacement uses only 8.5 Watts
- Indoor residential and commercial lighting
- 65W replacement
- 2700K
- Dimmable**
- Damp location



2 Pack displays, 24-2pks

Single pack displays, 48 lamps



LED 8.5W BR30 Reflector Display Packs

Item Number	Lamp Description	W	V	CRI	CCT	Lm	Base Type	M.O.L. (Inches)	Life/Hrs.	UPC	Pack/Master
S9148*	8.5BR30/LED/2700K/650L/120V/D	8.5	120	80	2700K	650	E26	5 3/16	25K	045923091483	48
S9149*	8.5BR30/LED/2700K/650L/120V/D/2PK	8.5	120	80	2700K	650	E26	5 3/16	25K	045923091490	24-2pks

** Consult Satco or visit www.satco.com for an up to date dimmer compatibility list.

Must be ordered in full cases only.

LED PAR LAMPS

**Familiar appearance.
High efficiency.
Direct replacements.**


**Introducing Satco LED PAR Lamps.
LED efficiency, indoors or out.**

Satco LED PAR lamps have the familiar look of the Halogen PAR lamps they replace, but deliver the high efficiency that only LEDs can. With the silvered reflector, traditional lens pattern, and exact dimensions of older Halogen PARs, Satco LED PARs represent an exact replacement. The only difference will be the greatly reduced energy and maintenance costs!

7W LED PAR20 lamps

Applications / Features

- 50W PAR20 replacement uses only 7 Watts
- Down lighting
- Track lighting
- Dimmable
- IP65 Listed - indoor/outdoor
- Approved for enclosed fixtures



LED PAR Lamps

Item Number	Lamp Description	W	V	CRI	CCT	Color Temp.	Lm	Bm	M.O.L. (Inches)	Life/Hrs.	UPC	Pack
LED PAR20 - Replaces 50W												
S9400*	7PAR20/LED/25/2700K/120V/SP	7	120	80	2700K	Warm White	500	25°	3 1/16	25K	045923094002	24/6
S9401*	7PAR20/LED/25/3000K/120V/SP	7	120	80	3000K	Soft White	500	25°	3 1/16	25K	045923094019	24/6
S9402*	7PAR20/LED/25/3500K/120V/SP	7	120	80	3500K	Neutral White	500	25°	3 1/16	25K	045923094026	24/6
S9403*	7PAR20/LED/25/4000K/120V/SP	7	120	80	4000K	Cool White	525	25°	3 1/16	25K	045923094033	24/6
S9404*	7PAR20/LED/25/5000K/120V/SP	7	120	80	5000K	Natural Light	525	25°	3 1/16	25K	045923094040	24/6
S9405*	7PAR20/LED/40/2700K/120V/FL	7	120	80	2700K	Warm White	500	40°	3 1/16	25K	045923094057	24/6
S9406*	7PAR20/LED/40/3000K/120V/FL	7	120	80	3000K	Soft White	500	40°	3 1/16	25K	045923094064	24/6
S9407*	7PAR20/LED/40/3500K/120V/FL	7	120	80	3500K	Neutral White	500	40°	3 1/16	25K	045923094071	24/6
S9408*	7PAR20/LED/40/4000K/120V/FL	7	120	80	4000K	Cool White	525	40°	3 1/16	25K	045923094088	24/6
S9409*	7PAR20/LED/40/5000K/120V/FL	7	120	80	5000K	Natural Light	525	40°	3 1/16	25K	045923094095	24/6




† Enclosed fixture rating - Effective on new production in June 2016

LED PAR LAMPS

13W LED PAR30 short neck lamps

Applications / Features

- 50W PAR30 short neck replacement uses only 13 Watts
- Down lighting
- Track lighting
- Dimmable
- IP65 Listed - indoor/outdoor
- Approved for enclosed fixtures



LED PAR Lamps

Item Number	Lamp Description	W	V	CRI	CCT	Color Temp.	Lm	Bm	M.O.L. (Inches)	Life/Hrs.	UPC	Pack
LED PAR30 Short Neck - Replaces 50W												
S9410*	13PAR30/SN/LED/25/2700K/120V/SP	13	120	80	2700K	Warm White	950	25°	3 5/8	25K	045923094101	12/6
S9411*	13PAR30/SN/LED/25/3000K/120V/SP	13	120	80	3000K	Soft White	950	25°	3 5/8	25K	045923094118	12/6
S9412*	13PAR30/SN/LED/25/3500K/120V/SP	13	120	80	3500K	Neutral White	950	25°	3 5/8	25K	045923094125	12/6
S9413*	13PAR30/SN/LED/25/4000K/120V/SP	13	120	80	4000K	Cool White	1000	25°	3 5/8	25K	045923094132	12/6
S9414*	13PAR30/SN/LED/25/5000K/120V/SP	13	120	80	5000K	Natural Light	1000	25°	3 5/8	25K	045923094149	12/6
S9415*	13PAR30/SN/LED/40/2700K/120V/FL	13	120	80	2700K	Warm White	950	40°	3 5/8	25K	045923094156	12/6
S9416*	13PAR30/SN/LED/40/3000K/120V/FL	13	120	80	3000K	Soft White	950	40°	3 5/8	25K	045923094163	12/6
S9417*	13PAR30/SN/LED/40/3500K/120V/FL	13	120	80	3500K	Neutral White	950	40°	3 5/8	25K	045923094170	12/6
S9418*	13PAR30/SN/LED/40/4000K/120V/FL	13	120	80	4000K	Cool White	1000	40°	3 5/8	25K	045923094187	12/6
S9419*	13PAR30/SN/LED/40/5000K/120V/FL	13	120	80	5000K	Natural Light	1000	40°	3 5/8	25K	045923094194	12/6
S9420*	13PAR30/SN/LED/60/2700K/120V/WFL	13	120	80	2700K	Warm White	950	60°	3 5/8	25K	045923094200	12/6
S9421*	13PAR30/SN/LED/60/3000K/120V/WFL	13	120	80	3000K	Soft White	950	60°	3 5/8	25K	045923094217	12/6
S9422*	13PAR30/SN/LED/60/3500K/120V/WFL	13	120	80	3500K	Neutral White	950	60°	3 5/8	25K	045923094224	12/6
S9423*	13PAR30/SN/LED/60/4000K/120V/WFL	13	120	80	4000K	Cool White	1000	60°	3 5/8	25K	045923094231	12/6
S9424*	13PAR30/SN/LED/60/5000K/120V/WFL	13	120	80	5000K	Natural Light	1000	60°	3 5/8	25K	045923094248	12/6




† Enclosed fixture rating - Effective on new production in June 2016

LED PAR LAMPS

13W LED PAR30 long neck lamps

Applications / Features

- 75W PAR30 long neck replacement uses only 13 Watts
- Down lighting
- Track lighting
- Dimmable
- IP65 Listed - indoor/outdoor
- Approved for enclosed fixtures



LED PAR Lamps



Item Number	Lamp Description	W	V	CRI	CCT	Color Temp.	Lm	Bm	M.O.L. (Inches)	Life/Hrs.	UPC	Pack
LED PAR30 Long Neck - Replaces 75W												
S9425*	13PAR30/LN/LED/25/2700K/120V/SP	13	120	80	2700K	Warm White	950	25°	4 1/16	25K	045923094255	12/6
S9426*	13PAR30/LN/LED/25/3000K/120V/SP	13	120	80	3000K	Soft White	950	25°	4 1/16	25K	045923094262	12/6
S9427*	13PAR30/LN/LED/25/3500K/120V/SP	13	120	80	3500K	Neutral White	950	25°	4 1/16	25K	045923094279	12/6
S9428*	13PAR30/LN/LED/25/4000K/120V/SP	13	120	80	4000K	Cool White	1000	25°	4 1/16	25K	045923094286	12/6
S9429*	13PAR30/LN/LED/25/5000K/120V/SP	13	120	80	5000K	Natural Light	1000	25°	4 1/16	25K	045923094293	12/6
S9430*	13PAR30/LN/LED/40/2700K/120V/FL	13	120	80	2700K	Warm White	950	40°	4 1/16	25K	045923094309	12/6
S9431*	13PAR30/LN/LED/40/3000K/120V/FL	13	120	80	3000K	Soft White	950	40°	4 1/16	25K	045923094316	12/6
S9432*	13PAR30/LN/LED/40/3500K/120V/FL	13	120	80	3500K	Neutral White	950	40°	4 1/16	25K	045923094323	12/6
S9433*	13PAR30/LN/LED/40/4000K/120V/FL	13	120	80	4000K	Cool White	1000	40°	4 1/16	25K	045923094330	12/6
S9434*	13PAR30/LN/LED/40/5000K/120V/FL	13	120	80	5000K	Natural Light	1000	40°	4 1/16	25K	045923094347	12/6
S9435*	13PAR30/LN/LED/60/2700K/120V/WFL	13	120	80	2700K	Warm White	950	60°	4 1/16	25K	045923094354	12/6
S9436*	13PAR30/LN/LED/60/3000K/120V/WFL	13	120	80	3000K	Soft White	950	60°	4 1/16	25K	045923094361	12/6
S9437*	13PAR30/LN/LED/60/3500K/120V/WFL	13	120	80	3500K	Neutral White	950	60°	4 1/16	25K	045923094378	12/6
S9438*	13PAR30/LN/LED/60/4000K/120V/WFL	13	120	80	4000K	Cool White	1000	60°	4 1/16	25K	045923094385	12/6
S9439*	13PAR30/LN/LED/60/5000K/120V/WFL	13	120	80	5000K	Natural Light	1000	60°	4 1/16	25K	045923094392	12/6

† Enclosed fixture rating - Effective on new production in June 2016

LED PAR LAMPS


15W & 18W LED PAR38 lamps

Applications / Features

- 90W, 100W PAR38 replacement uses only 15-18 Watts
- Down lighting
- Track lighting
- Dimmable
- IP65 Listed - indoor/outdoor



S9480 S9481 S9482 S9483 S9484



LED PAR Lamps

Item Number	Lamp Description	W	V	CRI	CCT	Color Temp.	Lm	Bm	M.O.L. (Inches)	Life/Hrs.	UPC	Pack
LED PAR38 - Replaces 90W												
S9440*	15PAR38/LED/25'/2700K/120V/SP	15	120	80	2700K	Warm White	1100	25°	5 3/16	25K	045923094408	12/6
S9441*	15PAR38/LED/25'/3000K/120V/SP	15	120	80	3000K	Soft White	1150	25°	5 3/16	25K	045923094415	12/6
S9442*	15PAR38/LED/25'/3500K/120V/SP	15	120	80	3500K	Neutral White	1150	25°	5 3/16	25K	045923094422	12/6
S9443*	15PAR38/LED/25'/4000K/120V/SP	15	120	80	4000K	Cool White	1200	25°	5 3/16	25K	045923094439	12/6
S9444*	15PAR38/LED/25'/5000K/120V/SP	15	120	80	5000K	Natural Light	1200	25°	5 3/16	25K	045923094446	12/6
S9445*	15PAR38/LED/40'/2700K/120V/FL	15	120	80	2700K	Warm White	1100	40°	5 3/16	25K	045923094453	12/6
S9446*	15PAR38/LED/40'/3000K/120V/FL	15	120	80	3000K	Soft White	1150	40°	5 3/16	25K	045923094460	12/6
S9447*	15PAR38/LED/40'/3500K/120V/FL	15	120	80	3500K	Neutral White	1150	40°	5 3/16	25K	045923094477	12/6
S9448*	15PAR38/LED/40'/4000K/120V/FL	15	120	80	4000K	Cool White	1200	40°	5 3/16	25K	045923094484	12/6
S9449*	15PAR38/LED/40'/5000K/120V/FL	15	120	80	5000K	Natural Light	1200	40°	5 3/16	25K	045923094491	12/6
S9450*	15PAR38/LED/60'/2700K/120V/WFL	15	120	80	2700K	Warm White	1100	60°	5 3/16	25K	045923094507	12/6
S9451*	15PAR38/LED/60'/3000K/120V/WFL	15	120	80	3000K	Soft White	1150	60°	5 3/16	25K	045923094514	12/6
S9452*	15PAR38/LED/60'/3500K/120V/WFL	15	120	80	3500K	Neutral White	1150	60°	5 3/16	25K	045923094521	12/6
S9453*	15PAR38/LED/60'/4000K/120V/WFL	15	120	80	4000K	Cool White	1200	60°	5 3/16	25K	045923094538	12/6
S9454*	15PAR38/LED/60'/5000K/120V/WFL	15	120	80	5000K	Natural Light	1200	60°	5 3/16	25K	045923094545	12/6
LED PAR38 - Replaces 100W												
S9455*	18PAR38/LED/40'/3000K/120V/FL	18	120	80	3000K	Soft White	1400	40°	5 3/16	25K	045923094552	12/6
S9456*	18PAR38/LED/40'/4000K/120V/FL	18	120	80	4000K	Cool White	1400	40°	5 3/16	25K	045923094569	12/6
LED PAR38 - Non-Dimmable 2 Pack - Replaces 90W												
S9457	15PAR38/LED/60'/3000K/120V/2PK	15	120	80	3000K	Soft White	1150	60°	5 3/16	25K	045923094576	8-2pks
LED PAR38 - Colors												
S9480	15PAR38/LED/40'/RED/120V	15	120	—	—	Red	—	40°	5 3/16	25K	045923094804	24/6
S9481	15PAR38/LED/40'/GREEN/120V	15	120	—	—	Green	—	40°	5 3/16	25K	045923094811	24/6
S9482	15PAR38/LED/40'/BLUE/120V	15	120	—	—	Blue	—	40°	5 3/16	25K	045923094828	24/6
S9483	15PAR38/LED/40'/AMBER/120V	15	120	—	—	Amber	—	40°	5 3/16	25K	045923094835	24/6
S9484	15PAR38/LED/40'/YELLOW/120V	15	120	—	—	Yellow	—	40°	5 3/16	25K	045923094842	24/6



† Enclosed fixture rating - Effective on new production in June 2016

LED PAR LAMPS

KolourOne Panel Array 2.0 7W PAR20 LED lamps

Applications / Features

- Indoor residential and commercial lighting
- Entertainment lighting
- Down lighting
- Display lighting
- Accent lighting
- Dimmable
- Replaces 50PAR20







KolourOne Panel Array 2.0 LED PAR20 Lamps

Item Number	Lamp Description	W	V	CRI	CCT	Lm	Bm	M.O.L. (Inches)	Life/ Hrs.	UPC	Pack
S8922*	7PAR20/LED/40/3500K/PA 2.0	7	120	83	3500K	435	40°	3 7/16	35K	045923089220	24/6
S8923	7PAR20/LED/40/5000K/PA 2.0	7	120	83	5000K	455	40°	3 7/16	35K	045923089237	24/6

KolourOne Panel Array 2.0 14W PAR30 short neck LED lamps

Applications / Features

- Indoor residential and commercial lighting
- Down lighting
- Display lighting
- Accent lighting
- Dimmable
- Replaces 75PAR30




KolourOne Panel Array 2.0 LED PAR30 Short Neck Lamps

Item Number	Lamp Description	W	V	CRI	CCT	Lm	Bm	M.O.L. (Inches)	Life/ Hrs.	UPC	Pack
S8936	14PAR30SN/LED/40/5000K/PA2.0	14	120	83	5000K	930	40°	3 5/8	35K	045923089367	12/6
S8941*	14PAR30SN/LED/60/2700K/PA2.0	14	120	84	2700K	860	60°	3 5/8	35K	045923089411	12/6
S8942*	14PAR30SN/LED/60/3500K/PA2.0	14	120	83	3500K	890	60°	3 5/8	35K	045923089428	12/6
S8943	14PAR30SN/LED/60/5000K/PA2.0	14	120	83	5000K	930	60°	3 5/8	35K	045923089435	12/6

KolourOne Panel Array 2.0 14W PAR30 long neck LED lamps

Applications / Features

- Indoor residential and commercial lighting
- Down lighting
- Display lighting
- Accent lighting
- Dimmable
- Replaces 75PAR30




KolourOne Panel Array 2.0 LED PAR30 Long Neck Lamps

Item Number	Lamp Description	W	V	CRI	CCT	Lm	Bm	M.O.L. (Inches)	Life/Hrs.	UPC	Pack
S8948*	14PAR30LN/LED/40/3500K/PA2.0	14	120	83	3500K	890	40°	4 ½	35K	045923089480	12/6
S8971*	14PAR30LN/LED/60/2700K/PA2.0	14	120	84	2700K	860	60°	4 ½	35K	045923089718	12/6
S8972*	14PAR30LN/LED/60/3500K/PA2.0	14	120	83	3500K	890	60°	4 ½	35K	045923089725	12/6
S9054*	14PAR30LN/LED/40/2700K/GU24	14	120	84	2700K	860	40°	4 ½	25K	045923090547	12/6

KolourOne Panel Array 2.0 17W PAR38 LED lamps

Applications / Features

- Indoor residential and commercial lighting
- Entertainment lighting
- Down lighting
- Display lighting
- Accent lighting
- Dimmable
- Replaces 90PAR38



KolourOne Panel Array 2.0 LED PAR38 Lamps

Item Number	Lamp Description	W	V	CRI	CCT	Lm	Bm	M.O.L. (Inches)	Life/Hrs.	UPC	Pack
S8977*	17PAR38/LED/40/2700K/PA 2.0	17	120	84	2700K	1120	40°	5 ½	35K	045923089770	12/6
S8984*	17PAR38/LED/60/2700K/PA 2.0	17	120	84	2700K	1120	60°	5 ½	35K	045923089848	12/6
S8985*	17PAR38/LED/60/3500K/PA 2.0	17	120	83	3500K	1160	60°	5 ½	35K	045923089855	12/6
S9060*	17PAR38/LED/40/2700K/GU24	17	120	84	2700K	1120	40°	5	25K	045923090608	12/6



LED PAR LAMPS

Ditto™ 7W LED PAR20 lamps

Same PAR20 shape.
Advanced LED technology!

Applications / Features

- Entertainment lighting
- Down lighting
- Display lighting
- Accent lighting
- Dimmable
- Damp location
- 7W PAR20 replaces 50PAR20



Ditto 7W PAR20 LED Lamps



Item Number	Lamp Description	W	V	CRI	CCT	Lm	Bm	M.O.L. (Inches)	Life/Hrs.	UPC	Pack
S9080*	7PAR20/LED/25°/3000K/120/D	7	120	80	3000K	415	25°	3 ¼	25K	045923090806	24/6
S9081	7PAR20/LED/25°/4000K/120/D	7	120	80	4000K	430	25°	3 ¼	25K	045923090813	24/6
S9083	7PAR20/LED/40°/4000K/120/D	7	120	80	4000K	430	40°	3 ¼	25K	045923090837	24/6

Ditto™ 11W LED PAR30 short neck lamps

Same PAR30 shape.
Advanced LED technology!

Applications / Features

- Entertainment lighting
- Down lighting
- Display lighting
- Accent lighting
- Dimmable
- Damp location
- 11W PAR30 replaces up to 75PAR30



Ditto 11W PAR30 LED Short Neck Lamps

Item Number	Lamp Description	W	V	CRI	CCT	Lm	Bm	M.O.L. (Inches)	Life/Hrs.	UPC	Pack
S9084*	11PAR30/SN/LED/25°/3000K/120/D	11	120	80	3000K	750	25°	3 ⅝	25K	045923090844	12/6
S9085*	11PAR30/SN/LED/25°/4000K/120/D	11	120	80	4000K	780	25°	3 ⅝	25K	045923090851	12/6
S9086*	11PAR30/SN/LED/40°/3000K/120/D	11	120	80	3000K	750	40°	3 ⅝	25K	045923090868	12/6
S9087*	11PAR30/SN/LED/40°/4000K/120/D	11	120	80	4000K	780	40°	3 ⅝	25K	045923090875	12/6



LED PAR LAMPS

Ditto™ 11W LED PAR30 long neck lamps

Same PAR30 shape.
Advanced LED technology!

Applications / Features

- Entertainment lighting
- Down lighting
- Display lighting
- Accent lighting
- Dimmable
- Damp location
- 11W PAR30 replaces up to 75PAR30



Ditto 11W PAR30 Long Neck LED Lamps



Item Number	Lamp Description	W	V	CRI	CCT	Lm	Bm	M.O.L. (Inches)	Life/Hrs.	UPC	Pack
S9088*	11PAR30/LN/LED/25°/3000K/120/D	11	120	80	3000K	750	25°	4 9/16	25K	045923090882	12/6
S9089	11PAR30/LN/LED/25°/4000K/120/D	11	120	80	4000K	780	25°	4 9/16	25K	045923090899	12/6
S9090*	11PAR30/LN/LED/40°/3000K/120/D	11	120	80	3000K	750	40°	4 9/16	25K	045923090905	12/6
S9091*	11PAR30/LN/LED/40°/4000K/120/D	11	120	80	4000K	780	40°	4 9/16	25K	045923090912	12/6

Ditto™ 17W LED PAR38 lamps

Same PAR38 shape.
Advanced LED technology!

Applications / Features

- Entertainment lighting
- Down lighting
- Display lighting
- Accent lighting
- Dimmable
- Damp location
- 17W PAR38 replaces 90PAR38



Ditto 17W PAR38 LED Lamps


Item Number	Lamp Description	W	V	CRI	CCT	Lm	Bm	M.O.L. (Inches)	Life/Hrs.	UPC	Pack
S9092*	17PAR38/LED/25°/3000K/120/D	17	120	80	3000K	1200	25°	5 3/16	25K	045923090929	12/6
S9093	17PAR38/LED/25°/4000K/120/D	17	120	80	4000K	1250	25°	5 3/16	25K	045923090936	12/6
S9094*	17PAR38/LED/40°/3000K/120/D	17	120	80	3000K	1200	40°	5 3/16	25K	045923090943	12/6
S9095	17PAR38/LED/40°/4000K/120/D	17	120	80	4000K	1250	40°	5 3/16	25K	045923090950	12/6

LED PAR16 & MR11 LAMPS

LED PAR16 4.5W & 6.5W lamps

Applications / Features

- 45W & 60W Halogen PAR16 lamp replacement uses only 4.5-6.5 Watts
- Indoor residential and commercial lighting
- Down lighting
- Accent lighting
- Pendant lighting
- Dimmable
- Damp location
- Approved for totally enclosed fixtures



Illumination at 3000K

	4.5W	6.5W
1m	525 lx in Center	730 lx in Center
2m	130 lx in Center	185 lx in Center

Beam Angle: 40°




LED PAR16 lamps

Item Number	Lamp Description	W	V	CRI	CCT	Lm	Bm	M.O.L. (Inches)	Life/Hrs.	UPC	Pack
S9386	4.5PAR16/LED/40°/3000K/120V	4.5	120	80	3000K	370	40°	2 7/8	25K	045923093869	12/1
S9387	4.5PAR16/LED/40°/5000K/120V	4.5	120	80	5000K	400	40°	2 7/8	25K	045923093876	12/1
S9388	6.5PAR16/LED/40°/3000K/120V	6.5	120	80	3000K	520	40°	2 7/8	25K	045923093883	12/1
S9389	6.5PAR16/LED/40°/5000K/120V	6.5	120	80	5000K	560	40°	2 7/8	25K	045923093890	12/1

3W, 12V LED MR11 lamps with GU4 base

Applications / Features

- Indoor residential and commercial lighting
- Down lighting
- Accent lighting
- Pendant lighting
- Non-dimmable
- Approved for totally enclosed fixtures



Illumination

	2700K	3000K	4000K	5000K
1m	700 lx in Center	730 lx in Center	760 lx in Center	800 lx in Center
2m	175 lx in Center	183 lx in Center	190 lx in Center	200 lx in Center

Beam Angle: 25°



3W, 12V LED MR11 Lamps With GU4 Base

Item Number	Lamp Description	W	V	CRI	CCT	Lm	Bm	M.O.L. (Inches)	Life/Hrs.	UPC	Pack
S9280	3MR11/LED/25°/2700K/12V	3	12	80	2700K	210	25°	1 1/2	25K	045923092800	12/1
S9281	3MR11/LED/25°/3000K/12V	3	12	80	3000K	220	25°	1 1/2	25K	045923092817	12/1
S9282	3MR11/LED/25°/4000K/12V	3	12	80	4000K	230	25°	1 1/2	25K	045923092824	12/1
S9283	3MR11/LED/25°/5000K/12V	3	12	80	5000K	240	25°	1 1/2	25K	045923092831	12/1

LED MR16 LAMPS



S9103, S9104,
S9105, S9106



S9380, S9381,
S9382, S9383,
S9384, S9385





S9490, S9491, S9492,
S9493, S9494, S9495,
S9496, S9497, S9498,
S9499, S9616

Available July 2016

MR16 LED lamps

Applications / Features

- Down lighting
- Accent lighting
- Pendant lighting
- Dimmable



MR16 LED Lamps



Item Number	Lamp Description	W	V	CRI	CCT	Lm	Bm	M.O.L. (Inches)	Life/ Hrs.	UPC	Pack
S9103*†	7MR16/LED/40'/27K/12V/D	7	12	80	2700K	500	40°	1 7/8	25K	045923091032	12/1
S9104*†	7MR16/LED/40'/3K/12V/D	7	12	80	3000K	520	40°	1 7/8	25K	045923091049	12/1
S9105†	7MR16/LED/40'/4K/12V/D	7	12	80	4000K	540	40°	1 7/8	25K	045923091056	12/1
S9106†	7MR16/LED/40'/5K/12V/D	7	12	80	5000K	560	40°	1 7/8	25K	045923091063	12/1
S9380*†	4.5MR16/LED/40'/30K/120V/GU10	4.5	120	80	3000K	370	40°	2 3/16	25K	045923093807	12/1
S9381†	4.5MR16/LED/40'/50K/120V/GU10	4.5	120	80	5000K	400	40°	2 3/16	25K	045923093814	12/1
S9382†	6.5MR16/LED/40'/27K/120V/GU10	6.5	120	80	2700K	500	40°	2 3/16	25K	045923093821	12/1
S9383*†	6.5MR16/LED/40'/30K/120V/GU10	6.5	120	80	3000K	520	40°	2 3/16	25K	045923093838	12/1
S9384†	6.5MR16/LED/40'/40K/120V/GU10	6.5	120	80	4000K	540	40°	2 3/16	25K	045923093845	12/1
S9385*†	6.5MR16/LED/40'/50K/120V/GU10	6.5	120	80	5000K	560	40°	2 3/16	25K	045923093852	12/1
S9490†**	6.5MR16/LED/25'/27K/12V	6.5	12	80	2700K	500	25°	1 3/4	25K	045923094903	12/1
S9491†**	6.5MR16/LED/25'/30K/12V	6.5	12	80	3000K	520	25°	1 3/4	25K	045923094910	12/1
S9492†	6.5MR16/LED/25'/35K/12V	6.5	12	80	3500K	530	25°	1 3/4	25K	045923094927	12/1
S9493†	6.5MR16/LED/25'/40K/12V	6.5	12	80	4000K	540	25°	1 3/4	25K	045923094934	12/1
S9494†	6.5MR16/LED/25'/50K/12V	6.5	12	80	5000K	560	25°	1 3/4	25K	045923094941	12/1
S9495†**	6.5MR16/LED/40'/27K/12V	6.5	12	80	2700K	500	40°	1 3/4	25K	045923094958	12/1
S9496†**	6.5MR16/LED/40'/30K/12V	6.5	12	80	3000K	520	40°	1 3/4	25K	045923094965	12/1
S9497†**	6.5MR16/LED/40'/35K/12V	6.5	12	80	3500K	530	40°	1 3/4	25K	045923094972	12/1
S9498†**	6.5MR16/LED/40'/40K/12V	6.5	12	80	4000K	540	40°	1 3/4	25K	045923094989	12/1
S9499†**	6.5MR16/LED/40'/50K/12V	6.5	12	80	5000K	560	40°	1 3/4	25K	045923094996	12/1
S9616†**	6.5MR16/LED/40'/30K/12V/90CRI	6.5	12	90	3000K	450	40°	1 3/4	25K	045923094965	12/1

All 12V MR16 lamps are compatible with electronic and magnetic transformers





**ENERGY STAR pending - August 2016

LED RECESSED DOWNLIGHT RETROFITS

5", 6" LED recessed downlight retrofits

Applications / Features

- Residential
- Office
- Retail
- Hospitality
- Solid state LED lighting
- Direct replacement for reflector lamps
- Dimmable**
- Long life, 50,000 hours
- High efficiency/Environmentally friendly
- Innovative design
- No UV or IR radiation
- 5 year warranty***
- c-UL-us damp location listed - Gimbal
- c-UL-us wet location listed - Baffle
- ENERGY STAR® certified



5/6" LED Recessed Downlight Retrofits



Item Number	Lamp Description	W	V	CRI	CCT	Lm	Bm	M.O.L. (Inches)	Life/Hrs.	UPC	Pack
S9469*	12WLED/RDL/5"-6"/27K/120V	12	120	90	2700K	800	90°	3 7/16	50K	045923094699	8/1
S9470*	12WLED/RDL/5"-6"/30K/120V	12	120	90	3000K	800	90°	3 7/16	50K	045923094705	8/1
S9471*	12WLED/RDL/5"-6"/40K/120V	12	120	90	4000K	840	90°	3 7/16	50K	045923094712	8/1
S9479*	12WLED/RDL/5"-6"/50K/120V	12	120	90	5000K	840	90°	3 7/16	50K	045923094798	8/1
S9475*	18WLED/RDL/5"-6"/27K/120V	18	120	90	2700K	1200	90°	3 7/16	50K	045923094750	8/1
S9476*	18WLED/RDL/5"-6"/30K/120V	18	120	90	3000K	1200	90°	3 7/16	50K	045923094767	8/1
S9477*	18WLED/RDL/5"-6"/40K/120V	18	120	90	4000K	1260	90°	3 7/16	50K	045923094774	8/1

5/6" LED Gimbal Retrofits

S9472*	12WLED/DIR/5"-6"/27K/120V	12	120	90	2700K	800	90°	4 1/4	50K	045923094729	8/1
S9473*	12WLED/DIR/5"-6"/30K/120V	12	120	90	3000K	800	90°	4 1/4	50K	045923094736	8/1
S9474*	12WLED/DIR/5"-6"/40K/120V	12	120	90	4000K	840	90°	4 1/4	50K	045923094743	8/1

**Consult Satco or visit www.satco.com for an up to date dimmer compatibility list.





***See separate warranty for complete terms and conditions. GU24 base sold separately, item number: S8999

LED RECESSED DOWNLIGHT RETROFITS

4" LED recessed downlight retrofits

Applications / Features

- Residential
- Office
- Retail
- Hospitality
- Solid state LED lighting
- Direct replacement for reflector lamps
- Dimmable**
- Long life, 50,000 hours
- High efficiency/Environmentally friendly
- No UV or IR radiation
- 5 year warranty***
- c-UL-us damp location listed - Gimbal
- c-UL-us wet location listed - Baffle
- ENERGY STAR® certified



4" LED Recessed Downlight Retrofits



Item Number	Lamp Description	W	V	CRI	CCT	Lm	Bm	M.O.L. (Inches)	Life/Hrs.	UPC	Pack
S9460*	9WLED/RDL/4"/27K/DIM/120V	9	120	90	2700K	600	90°	2 7/8	50K	045923094606	16/1
S9461*	9WLED/RDL/4"/30K/DIM/120V	9	120	90	3000K	600	90°	2 7/8	50K	045923094613	16/1
S9462*	9WLED/RDL/4"/40K/DIM/120V	9	120	90	4000K	600	90°	2 7/8	50K	045923094620	16/1
S9478*	9WLED/RDL/4"/50K/DIM/120V	9	120	90	5000K	630	90°	2 7/8	50K	045923094781	16/1
4" LED Gimbal Retrofits											
S9463*	9WLED/DIR/4"/40°/27K/120V	9	120	90	2700K	600	40°	3 5/16	50K	045923094637	8/1
S9464*	9WLED/DIR/4"/40°/30K/120V	9	120	90	3000K	600	40°	3 5/16	50K	045923094644	8/1
S9465*	9WLED/DIR/4"/40°/40K/120V	9	120	90	4000K	630	40°	3 5/16	50K	045923094651	8/1
S9466*	9WLED/DIR/4"/90°/27K/120V	9	120	90	2700K	600	90°	3 5/16	50K	045923094668	8/1
S9467*	9WLED/DIR/4"/90°/30K/120V	9	120	90	3000K	600	90°	3 5/16	50K	045923094675	8/1
S9468*	9WLED/DIR/4"/90°/40K/120V	9	120	90	4000K	630	90°	3 5/16	50K	045923094682	8/1


**Consult Satco or visit www.satco.com for an up to date dimmer compatibility list.
 ***See separate warranty for complete terms and conditions. GU10 base sold separately, item number: S9000

LED DECORATIVE LAMPS & RECESSED DOWNLIGHT RETROFITS

12V Recessed downlight retrofits

Applications / Features

- Residential • Office
- Retail • Hospitality
- Dimmable
- Damp location listed - Gimbal
- Wet location listed - Baffle
- Works with magnetic and electronic 12V transformers



Recessed Downlight Retrofits 12V

Item Number	Lamp Description	W	V	Base	CRI	CCT	Lm	Bm	M.O.L. (Inches)	Life/Hrs.	UPC	Pack
S9128	7WLED/RDL/3BFL/12V	7	12	GU5.3	90	3000K	400	90°	3	35K	045923091285	12/1
S9129	7WLED/RDL/4GBL/12V	7	12	GU5.3	90	3000K	430	90°	4	35K	045923091292	12/1
S9130	8WLED/RDL/4BFL/12V	8	12	GU5.3	90	3000K	460	90°	3 5/8	35K	045923091308	12/1

Decorative LED lamps

Applications / Features

- 25W candle replacement uses only 2.8 Watts
- 40W candle replacement uses only 4.5 Watts
- Accent lighting
- Pendant lighting
- Dimmable
- Damp location
- Approved for totally enclosed fixtures




S8951, S8952

S8950, S8953


S9200, S9201, S9202, S9203

Candle Beam Profile



Beam Angle: 120°

Globe Beam Profile




Beam Angle: 175°



Decorative LED Lamps

Item Number	Lamp Description	W	V	CRI	CCT	Lm	Bm	M.O.L. (Inches)	Life/Hrs.	UPC	Pack
S8950†	2.8CTC/LED/3000K/165L/120V	2.8	120	80	3000K	165	120°	3 3/4	25K	045923089503	12/1
S8951*†	4.5CTC/LED/2700K/E12/120V	4.5	120	80	2700K	300	120°	3 3/4	25K	045923089510	12/1
S8952*†	4.5CTC/LED/3000K/E12/120V	4.5	120	80	3000K	310	120°	3 3/4	25K	045923089527	12/1
S8953*†	4.5ETC/LED/3000K/E26/120V	4.5	120	80	3000K	310	120°	3 3/4	25K	045923089534	12/1
S9200*	6G25/LED/2700K	6	120	180	2700K	450	175°	4 1/4	25K	045923090523	24/6
S9201*	6G25/LED/3000K	6	120	180	3000K	470	175°	4 1/4	25K	045923090530	24/6
S9202	6G25/LED/4000K	6	120	180	4000K	490	175°	4 1/4	25K	045923090691	24/6
S9203	6G25/LED/5000K	6	120	180	5000K	510	175°	4 1/4	25K	045923092039	24/6



Freedom™ architectural LED downlights. High end features, not costs.

Hundreds of solutions, as easy as 1, 2, 3.

1 4" & 5-6" Light source housings in 2700K, 3000K, 4000K, 5000K all at 90CRI, and 2700K – 2200K warm dimming at 83CRI

2 4" Reflectors with 30°, 40°, 60° and 95° beam angles available 5"/6" Reflectors with 35°, 45°, 60° and 95° beam angles available

3 4 trim finishes – White, Bronze, Brushed Nickel, Polished Nickel

- LED-ready 4" & 5"-6" recessed can-type housings for new construction or remodeling available
- Unique right hand twist blade installation
- Dimmable
- Supplied with E26 socket adapter
- ENERGY STAR® Certified



Learn more about Freedom architectural downlights/retrofits in Satco catalog SA1710 or www.satco.com/catalogs and www.satco.com/freedom

LED SPECIALTY LAMPS

Carded specialty LED lamps

Applications / Features

- Sign bulbs
- Indicator
- Nightlights
- Decorative lamps
- Non-dimmable
- Direct replacements for incandescent & specialty lamps
- LED replacements use 80% less energy
- Wet location
- Long life; 25,000



Carded Specialty LED Lamps


Item Number	Lamp Description	W	Base	V	Finish	CCT	Lm	M.O.L. (Inches)	Life/Hrs.	UPC	Pack
S9150	1.4W A15/CL/LED/120V/CD	1.4	Med.	120	Clear	2700K	36	3 15/16	25K	045923091506	12/1
S9151	1.4W A15/FR/LED/120V/CD	1.4	Med.	120	Frost	2700K	45	3 15/16	25K	045923091513	12/1
S9152	1W CTC/LED/120V/CD	1.0	Cand.	120	Clear	2700K	25	3 9/16	25K	045923091520	12/1
S9153	1W CFC/LED/120V/CD	1.0	Cand.	120	Clear	2700K	25	3 7/8	25K	045923091537	12/1
S9154	1.4W ETC/LED/120V/CD	1.4	Med.	120	Clear	2700K	36	3 13/16	25K	045923091544	12/1
S9155	1W CTD/LED/CRYSTAL/120V/CD	1.0	Cand.	120	Clear	2700K	25	3 9/16	25K	045923091551	12/1
S9156	0.5W C7/CL/LED/120V/CD	0.5	Cand.	120	Clear	2700K	14	2 1/16	25K	045923091568	12/1
S9157	0.5W C7/WH/LED/120V/CD	0.5	Cand.	120	White	2700K	14	2 1/16	25K	045923091575	12/1
S9158	1.4W G16.5/CL/LED/120V/CD	1.4	Med.	120	Clear	2700K	36	2 3/4	25K	045923091582	12/1
S9159	1.4W G16.5/WH/LED/120V/CD	1.4	Med.	120	White	2700K	45	2 13/16	25K	045923091599	12/1
S9160	1.2W S11/CL/LED/120V/CD	1.2	Med.	120	Clear	2700K	32	2 5/16	25K	045923091605	12/1
S9161	1.2W S11/WH/LED/120V/CD	1.2	Med.	120	White	2700K	40	2 5/16	25K	045923091612	12/1
S9162	1.2W S11/BL/LED/120V/CD	1.2	Med.	120	Blue	—	—	2 5/16	25K	045923091629	12/1
S9163	1.2W S11/GR/LED/120V/CD	1.2	Med.	120	Green	—	—	2 5/16	25K	045923091636	12/1
S9164	1.2W S11/OR/LED/120V/CD	1.2	Med.	120	Orange	—	—	2 5/16	25K	045923091643	12/1
S9165	1.2W S11/RED/LED/120V/CD	1.2	Med.	120	Red	—	—	2 5/16	25K	045923091650	12/1
S9166	1.2W S11/Y/LED/120V/CD	1.2	Med.	120	Yellow	—	—	2 5/16	25K	045923091667	12/1
S9167	1.0W S11/CL/LED/E17/120V/CD	1.0	Inter.	120	Clear	2700K	28	2 5/16	25K	045923091674	12/1
S9168	1.0W S11/WH/LED/E17/120V/CD	1.0	Inter.	120	White	2700K	35	2 5/16	25K	045923091681	12/1
S9169	1.4W S14/Y/LED/120V/CD	1.4	Med.	120	Yellow	—	—	3 5/16	25K	045923091698	12/1
S9170	1.4W S14/RED/LED/120V/CD	1.4	Med.	120	Red	—	—	3 5/16	25K	045923091704	12/1
S9171	1.4W S14/GR/LED/120V/CD	1.4	Med.	120	Green	—	—	3 5/16	25K	045923091711	12/1
S9172	1.4W S14/BL/LED/120V/CD	1.4	Med.	120	Blue	—	—	3 5/16	25K	045923091728	12/1
S9173	1.4W S14/OR/LED/120V/CD	1.4	Med.	120	Orange	—	—	3 5/16	25K	045923091735	12/1
S9174	1.4W S14/CL/LED/120V/CD	1.4	Med.	120	Clear	2700K	36	3 5/16	25K	045923091742	12/1
S9175	1.4W S14/FR/LED/120V/CD	1.4	Med.	120	Frost	2700K	45	3 5/16	25K	045923091759	12/1
S9176	0.8W T6/FR/LED/120V/CD	0.8	Cand.	120	Frost	2700K	25	2 1/16	25K	045923091766	12/1
S9177	0.8W T6/CL/LED/120V/CD	0.8	Cand.	120	Clear	2700K	20	2 1/16	25K	045923091773	12/1

LED/CFL replacement lamps

Direct replacement for 4-pin* CFL's with electronic ballasts

Applications/ Features

- UL Classified 26 Watt direct replacement
- Works on 18, 26, 32, and 42 watt CFL ballasts*
- No re-wiring needed
- Instant on to full brightness / no flickering
- Vertical and horizontal options
- Up to 70% energy savings
- Long life - 50,000 hours
- 3 year warranty
- Dimmable**



LED/CFL Replacement Lamps



Item Number	Lamp Description	W	V	Base Type	CCT	CRI	M.O.L. (Inches)	Lm	Life/ Hrs.	UPC	Pack
S9300	13W/V/LED/CFL/827/4P	13	120-277	G24Q	2700K	80	3 5/8	900	50K	045923093005	50/10
S9301	13W/V/LED/CFL/835/4P	13	120-277	G24Q	3500K	80	3 5/8	900	50K	045923093012	50/10
S9302	13W/V/LED/CFL/840/4P	13	120-277	G24Q	4000K	80	3 5/8	925	50K	045923093029	50/10
S9303	13W/V/LED/CFL/850/4P	13	120-277	G24Q	5000K	80	3 5/8	950	50K	045923093036	50/10
S9304	13W/VL/LED/CFL/827/4P (Long)	13	120-277	G24Q	2700K	80	4 5/8	900	50K	045923093043	50/10
S9305	13W/VL/LED/CFL/835/4P (Long)	13	120-277	G24Q	3500K	80	4 5/8	900	50K	045923093050	50/10
S9306	13W/VL/LED/CFL/840/4P (Long)	13	120-277	G24Q	4000K	80	4 5/8	925	50K	045923093067	50/10
S9307	13W/VL/LED/CFL/850/4P (Long)	13	120-277	G24Q	5000K	80	4 5/8	950	50K	045923093074	50/10
S9308	13W/H/LED/CFL/827/4P	13	120-277	G24Q	2700K	80	5 1/4	900	50K	045923093081	50/10
S9309	13W/H/LED/CFL/835/4P	13	120-277	G24Q	3500K	80	5 1/4	900	50K	045923093098	50/10
S9310	13W/H/LED/CFL/840/4P	13	120-277	G24Q	4000K	80	5 1/4	925	50K	045923093104	50/10
S9311	13W/H/LED/CFL/850/4P	13	120-277	G24Q	5000K	80	5 1/4	950	50K	045923093111	50/10

* Fits G24q-2,3,4 sockets

** With compatible dimming ballasts

HIGH LUMEN LED LAMPS

Hi-Pro LED

High lumen, omni-directional lamps for industrial and commercial applications

Applications / Features

- Replaces HID, CFL, and Incandescent
- Direct wire range voltage 100-277V
- Approved for totally enclosed fixtures
- IP65 rated
- 3 CCT options
- Base up, base down or horizontal operation
- 5 Year limited warranty



High Lumen Industrial/Commercial LED Lamps



Item Number	Lamp Description	Replaces INC/CFL/HID	W	V	Base Type	CCT	Lm	M.O.L. (Inches)	Life/Hrs.	UPC	Pack/Mstr.
S9670	18W/LED/HID/2700K/100-277V	120/32/70	18	100-277	E26	2700K	2070	6 7/8	50K	045923096709	48
S9390	18W/LED/HID/5000K/100-277V	120/32/70	18	100-277	E26	5000K	2160	6 7/8	50K	045923093906	48
S9678	18W/LED/HID/AMBER/100-277V	—	18	100-277	E26	Amber	—	6 7/8	50K	045923096785	48
S9671	22W/LED/HID/2700K/100-277V	150/40/100	22	100-277	E26	2700K	2530	7 1/16	50K	045923096716	48
S9391	22W/LED/HID/5000K/100-277V	150/40/100	22	100-277	E26	5000K	2640	7 1/16	50K	045923093913	48
S9672	36W/LED/HID/2700K/100-277V	200/55/150	36	100-277	E26	2700K	4140	9 1/4	50K	045923096723	12
S9392	36W/LED/HID/5000K/100-277V	200/55/150	36	100-277	E26	5000K	4320	9 1/4	50K	045923093920	12
S9673*	45W/LED/HID/4000K/120-277V	300/65/175	45	100-277	EX39	4000K	5400	10 3/4	50K	045923096730	12
S9393*	45W/LED/HID/5000K/100-277V	300/65/175	45	100-277	EX39	5000K	5400	10 3/4	50K	045923093937	12
S9674*	54W/LED/HID/4000K/120-277V	300/85/250	54	100-277	EX39	4000K	6480	10 3/4	50K	045923096747	12
S9394*	54W/LED/HID/5000K/100-277V	300/85/250	54	100-277	EX39	5000K	6480	10 3/4	50K	045923093944	12
S9675*	80W/LED/HID/4000K/120-277V	400/100/320	80	100-277	EX39	4000K	9600	9 1/4	50K	045923096754	6
S9395*	80W/LED/HID/5000K/100-277V	400/100/320	80	100-277	EX39	5000K	9600	9 1/4	50K	045923093951	6
S9676*	100W/LED/HID/4000K/100-277V	500/150/400	100	100-277	EX39	4000K	12000	9 5/8	50K	045923096761	6
S9396*	100W/LED/HID/5000K/100-277V	500/150/400	100	100-277	EX39	5000K	12000	9 5/8	50K	045923093968	6
S9677*	120W/LED/HID/4000K/100-277V	750/200/600	120	100-277	EX39	4000K	14400	10 3/8	50K	045923096778	6
S9397*	120W/LED/HID/5000K/100-277V	750/200/600	120	100-277	EX39	5000K	14400	10 3/8	50K	045923093975	6

Accessories

92-406	Mog to Med Socket Reducer for S9390, S9391, S9392, S9670, S9671, S9672 and S9678	045923924064
80-929	Hard Wire Surge Protector	045923809293

Hi-Pro multi-beam LED lamps

High lumen, adjustable, multi-directional lamps for industrial and commercial applications

Applications / Features

- Replaces HID, CFL, and incandescent
- Direct wire range voltage 100-277V
- Approved for totally enclosed fixtures
- Hi bay or low bay
- Light panels lock into place creating 3 separate beam angle options
- IP65 rated
- 5 Year limited warranty



360° Beam



270° Beam



180° Beam

Available July 2016

High Lumen Multi-beam Industrial/Commercial LED Lamps



Item Number	Lamp Description	Replaces Inc/CFL/HID	W	V	Base Type	CCT	Lm	CRI	M.O.L. (Inches)	Life/Hrs.	UPC	Pack/Mstr.
S9750	30W/LED/HID/MB/5000K/100-277V	200/55/150	30	100-277	E26	5000K	3900	83	6 3/8	50K	045923097508	24
S9751	40W/LED/HID/MB/5000K/100-277V	300/65/175	40	100-277	EX39	5000K	5200	83	7 7/8	50K	045923097515	20
S9752	60W/LED/HID/MB/5000K/100-277V	500/105/250	60	100-277	EX39	5000K	7800	83	8 5/8	50K	045923097522	12

Accessories

92-406	Mog to Med Socket Reducer for S9751, S9752										045923924064	
80-929	Hard Wire Surge Protector										045923809293	

LED SPECIALTY LAMPS

LED elevator lamps

Applications / Features

- Elevator lighting
- Display lighting
- Non dimmable

Not for use with dimmers.

Recommended for use with magnetic transformers.

Compatibility with electronic transformers minimum load requirement must be verified.



S9005

S9004

LED Elevator Lamps

Item Number	Lamp Description	W	V	CRI	CCT	Lm	Bm	M.O.L. (Inches)	Life/Hrs.	UPC	Pack
S9005	2W/GBF/LED/12V/BA15D	2	12	80	3000K	120	40°	1 ¾	30K	045923090059	48/12
S9004	3W/1383/LED/12V/BA15S	3	12	80	3000K	120	40°	2 ½	30K	045923090042	48/12

Indoor use only. Not for use in totally enclosed fixtures.

LED replacements for Halogen G4, G9 and BA15S lamps

Applications / Features

- Solid state LED lighting
- High efficacy
- Long life
- Omni-directional light
- G9 Dimmable and non-dimmable
- G4, BA15S



S9226, S9227, S9228, S9229

S9220, S9221

S9222, S9223

S9224, S9225

LED Replacements for Halogen G4, G9 and BA15S Lamps



Item Number	Lamp Description	W	V	Base	CRI	CCT	Lm	M.O.L. (Inches)	Life/Hrs.	UPC	Pack
G4 Bi-Pin											
S9220	LED/2.3W/JC/G4/3000K	2.3	12	G4	80	3000K	180	1 ¾	15K	045923092206	50/1
S9221	LED/2.3W/JC/G4/5000K	2.3	12	G4	80	5000K	180	1 ¾	15K	045923092213	50/1
BA15S											
S9222	LED/2.3W/BA15S/3000K	2.3	12	BA15S	80	3000K	180	2	15K	045923092220	50/1
S9223	LED/2.3W/BA15S/5000K	2.3	12	BA15S	80	5000K	180	2	15K	045923092237	50/1
G9											
S9224*	LED/3.0W/G9/220L/3000K/DIM	3	120	G9	80	3000K	220	2 ⅞	15K	045923092244	50/1
S9225*	LED/3.0W/G9/220L/5000K/DIM	3	120	G9	80	5000K	220	2 ⅞	15K	045923092251	50/1
S9226	LED/5.0W/G9/450L/3000K	5	120	G9	80	3000K	450	2 ⅞	15K	045923092268	20/1
S9227	LED/5.0W/G9/450L/5000K	5	120	G9	80	5000K	450	2 ⅞	15K	045923092275	20/1
S9228*	LED/5.0W/G9/360L/3000K/DIM	5	120	G9	80	3000K	350	2 ⅞	15K	045923092282	20/1
S9229*	LED/5.0W/G9/360L/5000K/DIM	5	120	G9	80	5000K	350	2 ⅞	15K	045923092299	20/1

Silicon LED replacements for Halogen G4, G6.35, G9, GU5.3, MR11 and MR16 lamps

Applications / Features

- Solid state LED lighting
- High efficacy
- Long life
- Omni-directional light
- Dimmable



S9542,
S9543



S9544,
S9545



S9546,
S9547,



S9548,
S9549



S9550,
S9551



S9552,
S9553

Silicon LED Replacements for Halogen G4, G6.35, G9, MR11 and MR16 Lamps



Item Number	Lamp Description	W	V	Base	CRI	CCT	Lm	M.O.L. (Inches)	Life/ Hrs.	UPC	Pack
G4 Bi-Pin											
S9542	LED/1.6W/JC/G4/12V/3000K/200L/360°D	1.6	12	G4	80	3000K	200	1 7/16	25K	045923095429	20/200
S9543	LED/1.6W/JC/G4/12V/5000K/200L/360°D	1.6	12	G4	80	5000K	200	1 7/16	25K	045923095436	20/200
G6.35											
S9544	LED/3W/JC/G6.35/12V/3000K/300L/360°D	3	12	G6.35	80	3000K	300	1 5/8	25K	045923095443	20/200
S9545	LED/3W/JC/G6.35/12V/5000K/300L/360°D	3	12	G6.35	80	5000K	300	1 5/8	25K	045923095450	20/200
G9											
S9546	LED/1.6W/JCD/G9/120V/3000K/D	1.6	120	G9	80	3000K	200	1 7/8	25K	045923095467	20/200
S9547	LED/1.6W/JCD/G9/120V/5000K/D	1.6	120	G9	80	5000K	200	1 7/8	25K	045923095474	20/200
S9548	LED/4W/JCD/G9/120V/3000K/D	4	120	G9	80	3000K	480	2 7/16	25K	045923095481	20/200
S9549	LED/4W/JCD/G9/120V/5000K/D	4	120	G9	80	5000K	480	2 7/16	25K	045923095498	20/200
MR11											
S9550	LED/1.6MR11/40°/3000K/12V/D	1.6	12	G4	80	3000K	330	1 1/2	25K	045923095504	20/200
S9551	LED/1.6MR11/40°/5000K/12V/D	1.6	12	G4	80	5000K	330	1 1/2	25K	045923095511	20/200
MR16											
S9552	LED/3MR16/40°/3000K/12V/D	3	12	GU5.3	80	3000K	330	2	25K	045923095528	20/200
S9553	LED/3MR16/40°/5000K/12V/D	3	12	GU5.3	80	5000K	330	2	25K	045923095535	20/200

LED T8 LAMPS

Satco 2', 3' & 6" U-bend LED T8 lamps

Direct replacement for linear
or U-bend T8 fluorescent lamps
in existing fixtures with instant
or rapid start ballasts.
No rewiring required**

Applications / Features

- Over 40% energy savings vs. standard T8 systems
- All glass tube - eliminating the possibility of yellowing
- Direct replacement solution allows the fixture to maintain the Original UL and CSA Compliance
- Long life- 50,000 hours
- Instant on to full brightness / no flicker
- 2 ft. DLC - listed
- U-bend - NSF certified, shatterproof coated
- Damp location
- 5 year warranty



LED T8 Fluorescent 2', 3' & 6" U-Bend Replacement Lamps

Item Number	Lamp Description	W	CRI	Base Type	Bm	CCT	Lm	M.O.L. (Inches)	Life/Hrs.	UPC	Pack
2' LED T8											
S9746*	9T8/LED/24-830/DR	9	82	Med Bi-Pin	230°	3000K	1150	24	50K	045923097461	10
S9747*	9T8/LED/24-835/DR	9	82	Med Bi-Pin	230°	3500K	1150	24	50K	045923097478	10
S9748*	9T8/LED/24-840/DR	9	82	Med Bi-Pin	230°	4000K	1150	24	50K	045923097485	10
S9749*	9T8/LED/24-850/DR	9	82	Med Bi-Pin	230°	5000K	1150	24	50K	045923097492	10
3' LED T8											
S9790	11T8/LED/36-830/DR	11	82	Med Bi-Pin	230°	3000K	1450	36	50K	045923097904	10
S9791	11T8/LED/36-835/DR	11	82	Med Bi-Pin	230°	3500K	1450	36	50K	045923097911	10
S9792	11T8/LED/36-840/DR	11	82	Med Bi-Pin	230°	4000K	1450	36	50K	045923097928	10
S9793	11T8/LED/36-850/DR	11	82	Med Bi-Pin	230°	5000K	1450	36	50K	045923097935	10
U-Bend 6" LED T8											
S9294†	12T8U6/LED/22.5-830/DR	12	82	Med Bi-Pin	230°	3000K	1800	22.5	50K	045923092947	12
S9295†	12T8U6/LED/22.5-835/DR	12	82	Med Bi-Pin	230°	3500K	1800	22.5	50K	045923092954	12
S9296†	12T8U6/LED/22.5-840/DR	12	82	Med Bi-Pin	230°	4000K	1800	22.5	50K	045923092961	12
S9297†	12T8U6/LED/22.5-850/DR	12	82	Med Bi-Pin	230°	5000K	1800	22.5	50K	045923092978	12

** May not be compatible with all ballasts. Visit www.satco.com for an approved list.

LED T8 LAMPS

Satco 14W, 4' LED T8 lamps

Direct replacement for linear fluorescent T8 lamps in existing fixtures with instant or rapid start ballasts. No rewiring required*

Applications/ Features

- Over 40% energy savings vs standard 4' T8 systems
- All glass tube - eliminating the possibility of yellowing
- Direct replacement solution allows the fixture to maintain the Original UL and CSA Compliance
- Long life- 50,000 hours
- Instant on to full brightness / no flicker
- Damp location
- UL listed
- DLC listed
- 5 year warranty



LED Fluorescent Replacement Lamps

Item Number	Lamp Description	W	CRI	Base Type	Bm	CCT	Lm	M.O.L. (Inches)	Life/ Hrs.	UPC	Pack
S9734*	14T8/LED/48-830/DR	14	82	Med Bi-Pin	230°	3000K	1800	48	50K	045923097348	10
S9735*	14T8/LED/48-835/DR	14	82	Med Bi-Pin	230°	3500K	1800	48	50K	045923097355	10
S9736*	14T8/LED/48-840/DR	14	82	Med Bi-Pin	230°	4000K	1800	48	50K	045923097362	10
S9737*	14T8/LED/48-850/DR	14	82	Med Bi-Pin	230°	5000K	1800	48	50K	045923097379	10

* May not be compatible with all rapid start, dimmable, and emergency ballasts. Visit www.satco.com for an approved list.

Satco 17W, 4' LED T8 lamps

Direct replacement for linear fluorescent T8 lamps in existing fixtures with instant or rapid start ballasts. No rewiring required*

Applications/ Features

- Over 40% energy savings vs standard 4' T8 systems
- All glass tube eliminates the possibility of yellowing
- Direct replacement solution allows the fixture to maintain the Original UL and CSA Compliance
- Long life- 50,000 hours
- Instant on to full brightness / no flicker
- Damp location
- DLC listed
- 5 year warranty



LED Fluorescent Replacement Lamps

Item Number	Lamp Description	W	CRI	Base Type	Bm	CCT	Lm	M.O.L. (Inches)	Life/ Hrs.	UPC	Pack
S9775*	17T8/LED/48-830/DR	17	80	Med Bi-Pin	230°	3000K	2200	48	50K	045923097751	10
S9776*	17T8/LED/48-835/DR	17	80	Med Bi-Pin	230°	3500K	2200	48	50K	045923097768	10
S9777*	17T8/LED/48-840/DR	17	80	Med Bi-Pin	230°	4000K	2200	48	50K	045923097775	10
S9778*	17T8/LED/48-850/DR	17	80	Med Bi-Pin	230°	5000K	2200	48	50K	045923097782	10

* May not be compatible with all rapid start, dimmable, and emergency ballasts. Visit www.satco.com for an approved list.

LED T8 LAMPS

Satco By-pass 15W LED T8 lamps

Direct wire replacement for linear fluorescent T8 lamps in existing fixtures.

Applications/ Features

- No ballast or external driver required
- Direct wire 120-277V line voltage*
- All glass tube
- -20°C (-4°F) to 45°C (113°F) - ambient operating temperature
- Long life: 50,000 hours
- Damp location
- c-UL-us classified
- 5 year warranty
- DLC listed

LED fluorescent replacement lamps



Item Number	Lamp Description	W	CRI	Base Type	Bm	CCT	Lm	M.O.L. (Inches)	Life/ Hrs.	UPC	Pack
S9720	15T8/LED/48-830/BP	15	82	Med Bi-Pin	230°	3000K	1700	48	50K	045923097201	10
S9721	15T8/LED/48-835/BP	15	82	Med Bi-Pin	230°	3500K	1700	48	50K	045923097218	10
S9722	15T8/LED/48-840/BP	15	82	Med Bi-Pin	230°	4000K	1800	48	50K	045923097225	10
S9723	15T8/LED/48-850/BP	15	82	Med Bi-Pin	230°	5000K	1800	48	50K	045923097232	10

* Install only in non-shunted lampholders

Satco 33W, 8' LED T8 lamps

Direct replacement for linear fluorescent T8 lamps in existing fixtures with electronic instant start ballasts. No rewiring required*

Applications/ Features

- Over 40% energy savings vs standard 8' T8 systems
- All glass tube eliminates the possibility of yellowing
- Direct replacement solution allows the fixture to maintain the Original UL and CSA Compliance
- Long life- 50,000 hours
- Damp location
- Instant on to full brightness / no flicker
- 5 year warranty



LED Fluorescent Replacement Lamps

Item Number	Lamp Description	W	CRI	Base Type	Bm	CCT	Lm	M.O.L. (Inches)	Life/ Hrs.	UPC	Pack
S9700	33T8/LED/96-840/DR	33	82	Single Pin	230°	4000K	4400	96	50K	045923097003	10
S9701	33T8/LED/96-850/DR	33	82	Single Pin	230°	5000K	4400	96	50K	045923097010	10

* May not be compatible with all rapid start ballasts. Visit www.satco.com for an approved list.

Satco 25W, 4' LED T5 lamps

Direct replacement for linear fluorescent F54T5 lamps in existing fixtures with electronic ballasts. No rewiring required*

Applications/ Features

- Over 50% energy savings vs standard 4' T5 systems
- All glass tube - eliminating the possibility of yellowing
- Direct replacement solution allows the fixture to maintain the Original UL and CSA Compliance
- Long life- 50,000 hours
- Damp location
- Instant on to full brightness / no flicker
- Damp location
- UL classified
- DLC listed
- 5 year warranty



LED Fluorescent Replacement Lamps

Item Number	Lamp Description	W	CRI	Base Type	Bm	CCT	Lm	M.O.L. [†] (Nominal)	Life/ Hrs.	UPC	Pack
S9712	25T5/LED/46-835/DR	25	82	Mini Bi-Pin	185°	3500K	3200	48	50K	045923097126	10
S9710	25T5/LED/46-840/DR	25	82	Mini Bi-Pin	185°	4000K	3200	46 (48)	50K	045923097102	10
S9711	25T5/LED/46-850/DR	25	82	Mini Bi-Pin	185°	5000K	3200	46 (48)	50K	045923097119	10

* May not be compatible with all rapid start ballasts. Visit www.satco.com for an approved list.

Blink™ LED fixtures.

LED efficiency.
Simple to install.
Battery backup options.



7" Square Blink



5.5" Round Blink



9" Square Blink
with optional battery
backup module



7" Round Blink
with optional battery
backup module

Blink LED fixtures

- 5.5", 7", 9" Round or square at 10.5, 13.5 and 18.5 Watts respectively
- 13" Round at 25 Watts
- 5"x18", 7"x18" rectangles at 16 and 24 Watts respectively
- Wide, 108° beam pattern
- 2700K, 3000K, 5000K versions
- Dimmable
- Damp location listed
- Wet location models available
- Simple 1, 2, 3 installation
- 5.5", 7", 9" fit 3" and 4" junction boxes
- White, Brushed Nickel or Bronze finish
- ENERGY STAR certified

Battery backup modules

- Available for 7" and 9" round or square fixtures, available in white
- 24 Hour recharge time
- 90 Minute operation from battery
- Switching time < 1 second
- Over-charge/discharge protection
- Self-checking function
- Test button
- Blink fixtures sold separately



Satco. Lighting the future for the past 50 years.

Learn more about Blink LED fixtures in Satco catalog SA1696 or www.satco.com/catalogs

SIMPLE. FUNCTIONAL. CONSISTENT. RELIABLE.

Introducing Thread linear LED under-cabinet and cove lighting system.




Features

- Exact fixture to fixture color temperature
- Exact fixture to fixture LED spacing for consistent, even lighting
- Simple to install and connect
- Self-driven, no external driver required
- Capable of 65' continuous runs off one power feed
- Diffuser lens for even light – eliminates hot spots and glare
- Available in 6", 10", 21" and 30" lengths
- Sleek design; less than 1" square!
- 120V direct power feed
- 2700K or 3500K
- Over 300 lumens per lineal foot
- Dimmable
- Very low heat, no UV or IR radiation
- Designed for direct-wire or portable installations
- Many power and connection accessories available
- 50,000 hour life
- ENERGY STAR certified for under-cabinet and cove applications



THREAD™ LINEAR LED SYSTEM



Consistent 0.5" LED package spacing at fixture connections

Learn more about Thread LED under cabinet and cove lighting systems in NUVO Lighting catalog NU1185 or www.satco.com/catalogs

