



WAC

LANDSCAPE LIGHTING

2017

Which do you NEED? ONE or DOZENS?

WAC LED One Size Fits All

Allows all brightness and beam spread adjustments to be made in the field.
Replaces the need for MR16 Halogen
(Patent Pending)



Adjustable 10° to 60° Beam
2W to 16W adjustability
190 to 1045 Lumens




=

4W
170 Lumens

6.5W
348 Lumens

13W
590 Lumens

21W
993 Lumens



Equivalent to 10-50W MR16 Halogen












Adjustable 15° to 60° Beam
2W to 12W adjustability
70 to 505 Lumens

=

4W
170 Lumens

6.5W
348 Lumens


14W
590 Lumens





Durability. Flexibility.

Every WAC Lighting fixture in our patent pending line of technology landscape products is thoroughly tested in our nationally recognized NVLAP, UL, and ETL certified laboratories for safety, durability, and robust long term performance even in the most rugged environments.

 Listed to UL 1838 standard (12V)
1598 standard (120V)



LED Life Expectancy

Rated life of LED lights are based on IES (Illuminating Engineering Society) L70 standard accelerated lifetime testing for how long they will operate until only 70% of the original light output remains .

What IP RATINGS mean for YOU and your CUSTOMERS

Ingress Protection ratings tell you how a fixture is tested to hold up under different conditions.



IP44 Protected from water spray from any direction.



IP65 Protected from low pressure water jets from any direction.



IP66 Protected from high pressure water jets from any direction.



IP67 Protected from short periods of immersion up to 3.2 feet in depth



IP68 Protected from long periods of immersion up to 5 feet in depth

Don't Compromise

The cutting edge technology you have been waiting for, and never have to do without again.
Available in a full range of landscape lighting fixtures in warm white and pure white light.



WAC

It's all
about the
DETAILS



OTHER BRANDS

Gone are the appearance of LED diodes.
Enjoy the light, without the many glary dots.

Quality LED Illumination comparable to Incandescent
without the pain of a high electricity bill.
Light output ranges adjust comparably to anywhere
from 10W to 75W MR16 Halogen fixtures.

Materials that mean business

Marine Grade
Diecast Stainless Steel

Diecast Brass

Corrosion Resistant
Diecast Aluminum

Unlike other brands of landscape lighting,
we fabricate each product ourselves to a component level.
Using the best UV and corrosion resistant materials available to be able to confidently
support a true 10 year warranty.

LANDSCAPE

FROM DRY TO WET TO UNDERWATER ALL ON ONE TRANSFORMER

Cohesively engineered to work together and make installation a snap.



Wall Wash
Variable wattage control and patent pending wide optical distribution



Deck Light
3 functional casted designs



3" Inground
Durable construction with unique features for maintaining uniformity



Hardscape
Easily adapts to any hardscape, step, deck or bench applications

A TEAM EFFORT

From our fully adjustable integrated LED accent light to our submersible in-grounds, every product is engineered to work well together as a fully integrated solution. We have everything you need whether you're lighting a small jewel of a garden or a sublime outdoor oasis, all connected to the same transformer.



Outdoor Landscape Tape
IP68 and perfect for all landscape applications in or out of water



Accent
Variable wattage control and beam adjustability



1" & 2" Recessed
IP68, adapts to inground or recessed installations



Submersible
IP68 rated for underwater or other wet applications



Step Light
Extra light where it's needed the most



Bollard, Area & Path Lights
Garden spaces and pathways

ACCENT LED LANDSCAPE

Continuously Adjustable
Brightness Control
Indexed at
2W, 4W, 8W, 13W, 16W

Continuously Adjustable Beam Angles
Indexed at
10°, 25°, 40°, 60°

- Adjustable beam angle
- IP66 rated, Protected against high-pressure water jets
 - Includes a detachable shroud
- Solid diecast brass or corrosion resistant aluminum
 - Factory sealed water tight fixtures
- Constant output for 9V-15V or 110V-120V input
 - Can be used as an uplight or downlight

ACCENT LED LANDSCAPE



1838 listed (12V)
1598 listed (120V)

12V

*Integral Brightness Control
Adjustable beam angle 10° to 60°*

*One Fixture replaces all older
halogen landscape accent lights.*

Transformer Required (order separately)


Input	9 - 15VAC
Power	2W to 16W / 2VA - 23VA
Brightness	190 lm to 1045 lm
Beam Angle	10° to 60°
CRI	85
Rated Life	70,000 hours

2700K *Warm White*

5011-27BZ *Bronze on Aluminum*
5011-27BBR *Bronze on Brass*

3000K *Pure White*

5011-30BZ *Bronze on Aluminum*
5011-30BBR *Bronze on Brass*



*Mounting stake (12V),
Detachable shroud, 6' lead wire and
direct burial gel filled wire nuts (12V)
or standard wire nuts (120V) included*

120V

*Integral Brightness Control
Adjustable beam angle 15° to 60°*

*Simple to retrofit existing
line voltage systems or coordinate well
with a new commercial landscape job*











Input	110V - 120VAC
Power	3.5W to 14.5W
Brightness	100 lm to 900 lm
Beam Angle	15° to 60°
CRI	85
Rated Life	45,000 hours

3000K *Pure White*

5012-30BZ *Bronze on Aluminum*
5012-30BBR *Bronze on Brass*

See pages 17-18 for  color changing accent lights

Accessories

6" Long Shroud		5010-LSHR-BZ 5010-LSHR-BBR	Bronze on Aluminum Bronze on Brass	Reduce glare. Ideal for downlighting application
Additional Stake		9000-ST9-BK	Bronze	Durable PC stake
Surface Mount Flange/Stake		5000-SCP-BZ 5000-SCP-BBR	Bronze on Aluminum Bronze on Brass	Includes three 7 inch threaded stainless steel stabilizing pins for ground mounting or surface mounts with four screws or over a junction box
Guardian Mount		9000-SP9-BZ	Stainless Steel	Heavy duty stainless steel spike to position fixture Formed from a single piece of metal
Gutter Mount Bracket		5000-GM-BZ	Stainless Steel	Stainless Steel universal mounting bracket for gutter mounting fixture
Power Stake		9000-RPT-BK	Black	Easy wiring accessory designed for 120V products; eliminates the need for a separate J-box.
Tree Mount Junction Box		5000-TCP-BZ	Bronze on Aluminum	Bronze on Aluminum box with Stainless steel mounting screws. Two 1/2" NPT threaded holes
Optics		LENS-20-AMB Amber LENS-20-GRN Green LENS-20-RED Red	LENS-20-BLU Blue LENS-20-FR Frosted LENS-20-SPR Spread	LENS-20-BEL Beam Elongating Enhances saturation of florals and foliage
Extension Rods		5000-X04-BZ 4 in 5000-X08-BZ 8 in 5000-X12-BZ 12 in	5000-X18-BZ 18 in 5000-X24-BZ 24 in	Extends distance between Accent light and Surface Mount Canopy, Stake, or Tree Mount box
Rod L-Coupler		5000-LCO-BZ	Bronze	

MINI ACCENT LED LANDSCAPE

Continuously Adjustable Beam Angles
Indexed at
10°, 25°, 40°, 50°

Continuously Adjustable
Brightness Control
Indexed at
1W, 2W, 4W, 6W, 7W



- Adjustable beam angle
- IP66 rated, Protected against high-pressure water jets
 - Includes a detachable shroud
- Solid diecast brass or corrosion resistant aluminum
 - Factory sealed water tight fixtures
 - Constant output for 9V-15V input
- Can be used as an uplight or downlight
 - 2700K or 3000K color temperature

MINI ACCENT LED LANDSCAPE



12V

*Integral Brightness Control
Adjustable beam angle 10° to 50°
One Fixture replaces all older
halogen landscape accent light.*


*Transformer Required
(order separately)*

Input Power	9 -15VAC
Brightness	1W to 7W / 2VA -10.5VA
Beam Angle	45 lm to 365 lm
CRI	10° to 50°
Rated Life	85
	70,000 hours

*Mounting stake (12V),
Detachable shroud, 6' lead wire and
direct burial gel filled wire nuts (12V)*



Continuously Adjustable
Brightness Control



Single and Double Stem Mount
available. See pages 53-54



Shown with
gutter mount bracket
accessory

2700K *Warm White*

5111-27BZ *Bronze on Aluminum*
5111-27BBR *Bronze on Brass*

3000K *Pure White*

5111-30BZ *Bronze on Aluminum*
5111-30BBR *Bronze on Brass*

Accessories

5" Long Shroud		5111-LSHR-BZ 5111-LSHR-BBR	<i>Bronze on Aluminum</i> <i>Bronze on Brass</i>	<i>Reduce glare. Ideal for downlighting application</i>
Additional Stake		9000-ST9-BK	<i>Bronze</i>	<i>Durable PC stake</i>
Surface Mount Flange/Stake		5000-SCP-BZ 5000-SCP-BBR	<i>Bronze on Aluminum</i> <i>Bronze on Brass</i>	<i>Includes three 7 inch threaded stainless steel stabilizing pins for ground mounting or surface mounts with four screws or over a junction box</i>
Guardian Mount		9000-SP9-BZ	<i>Stainless Steel</i>	<i>Heavy duty stainless steel spike to position fixture Formed from a single piece of metal</i>
Gutter Mount Bracket		5000-GM-BZ	<i>Stainless Steel</i>	<i>Stainless Steel universal mounting bracket for gutter mounting fixture</i>
Tree Mount Junction Box		5000-TCP-BZ	<i>Bronze on Aluminum</i>	<i>Bronze on Aluminum box with Stainless steel mounting screws. Two 1/2" NPT threaded holes</i>
Optics		LENS-16-AMB LENS-16-GRN LENS-16-RED LENS-16-BLU	<i>Amber</i> <i>Green</i> <i>Red</i> <i>Blue</i>	LENS-16-FR <i>Frosted</i> LENS-16-SPR <i>Spread</i> LENS-16-BEL <i>Elongating</i> <i>Enhances saturation of florals and foliage</i>
Extension Rods		5000-X04-BZ 5000-X08-BZ 5000-X12-BZ	<i>4 in</i> <i>8 in</i> <i>12 in</i>	5000-X18-BZ <i>18 in</i> 5000-X24-BZ <i>24 in</i> <i>Extends distance between Accent light and Surface Mount Canopy, Stake, or Tree Mount box</i>
Rod L-Coupler		5000-LCO-BZ	<i>Bronze</i>	

WALL WASH LED LANDSCAPE

Patent Pending Optical Design
Even coverage at
15° upwards, 50° x 80°

**Continuously Adjustable
Brightness Control**
Indexed at
2W, 4W, 8W, 13W, 16W

- A uniform wide distribution wall wash from a small form factor
 - IP66 rated, Protected against powerful water jets
 - Solid diecast brass or corrosion resistant aluminum alloy
 - Factory sealed water tight fixtures
 - Constant output for 9V-15V, 110V - 120V inputs

WALL WASH LED LANDSCAPE



1838 listed (12V)
1598 listed (120V)

12V

*Integral Brightness Control
Transformer Required
(order separately)*

Input	9 - 15VAC
Power	2W to 16W / 2 - 23VA
Brightness	190 lm to 980 lm
Beam Angle	15° upward (50° by 80°)
CRI	85
Rated Life	70,000 hours



120V

Integral Brightness Control


Input	110V - 120VAC
Power	3.5W to 14.5W
Brightness	95 lm to 855 lm
Beam Angle	15° upward (50° by 80°)
CRI	85
Rated Life	45,000 hours

2700K *Warm White*

5021-27BZ *Bronze on Aluminum*
5021-27BBR *Bronze on Brass*

3000K *Pure White*

5021-30BZ *Bronze on Aluminum*
5021-30BBR *Bronze on Brass*



*Mounting stake (12V),
6' lead wire and direct burial
gel filled wire nuts (12V) or
standard wire nuts (120V) included*

3000K *Pure White*

5022-30BZ *Bronze on Aluminum*
5022-30BBR *Bronze on Brass*

See pages 17-18 for *color changing wall wash lights*

Accessories


<i>Additional Stake</i>		9000-ST9-BK	<i>Bronze</i>	<i>Durable PC stake</i>		
<i>Surface Mount Flange/Stake</i>		5000-SCP-BZ 5000-SCP-BBR	<i>Bronze on Aluminum</i> <i>Bronze on Brass</i>	<i>Includes three 7 inch threaded stainless steel stabilizing pins for ground mounting or surface mounts with four screws or over a junction box</i>		
<i>Guardian Mount</i>		9000-SP9-BZ	<i>Stainless Steel</i>	<i>Heavy duty stainless steel spike to position fixture Formed from a single piece of metal</i>		
<i>Gutter Mount Bracket</i>		5000-GM-BZ	<i>Stainless Steel</i>	<i>Stainless Steel universal mounting bracket for gutter mounting fixture</i>		
<i>Power Stake</i>		9000-RPT-BK	<i>Black</i>	<i>Easy wiring accessory designed for 120V products; eliminates the need for a separate J-box.</i>		
<i>Tree Mount Junction Box</i>		5000-TCP-BZ	<i>Bronze on Aluminum</i>	<i>Bronze on Aluminum box with Stainless steel mounting screws. Two 1/2" NPT threaded holes</i>		
<i>Optics</i>		LENS-2X4-AMB LENS-2X4-GRN LENS-2X4-RED	<i>Amber</i> <i>Green</i> <i>Red</i>	LENS-2X4-BLU LENS-2X4-FR LENS-2X4-SPR	<i>Blue</i> <i>Frosted</i> <i>Spread</i>	<i>Enhances saturation of florals and foliage and turtle friendly</i>
<i>Extension Rods</i>		5000-X04-BZ 5000-X08-BZ 5000-X12-BZ	<i>4 in</i> <i>8 in</i> <i>12 in</i>	5000-X18-BZ 5000-X24-BZ	<i>18 in</i> <i>24 in</i>	<i>Extends distance between Accent light and Surface Mount Canopy, Stake, or Tree Mount box</i>
<i>Rod L-Coupler</i>		5000-LCO-BZ	<i>Bronze</i>			



3" Inground

- Tilt and adjust beam angles
- Integral brightness control
- IP67 rated, Protected from temporary immersion under water
 - Drive over up to 4500lbs
- Solid diecast brass or corrosion resistant cast aluminum
 - Available concrete pour kit
- Constant output for 9V-15V or 110V-120V inputs


3" Inground Features




Typical Inground
 Most light output goes into the air,
 causing light pollution



Adjust Beam Angles
 Presets at
 15°, 30°, 45°, 60°




Adjustable WAC Inground
 Adjust the light to where you need it



Typical Inground
 Most light output goes into the air,
 causing light pollution



Tilt and Aim
 Up to 40° of adjustability preset at
 -20°, -10°, 0°, 10°, 20°



Adjustable WAC Inground
 Adjust the light to where you need it



Control Brightness
 Adjustable from 70lm to 505lm
 Presets Comparable to
 10W, 25W, 35W, 50W, 75W Halogen source



3" INGROUND LED LANDSCAPE





3" INGROUND LED LANDSCAPE

IP67


12V

*Integral Brightness Control
Adjustable beam angle
Directional aim with +/- 20° Tilt*

Input	9-15VAC
Power	2W to 12W / 2-17VA
Brightness	70 lm to 505 lm
Beam Angle	15° to 60°
CRI	85
Rated Life	55,000 hours

2700K *Warm White*
5031-27BZ | Bronze on Aluminum
5031-27BBR | Bronze on Brass

3000K *Pure White*
5031-30BZ | Bronze on Aluminum
5031-30BBR | Bronze on Brass



*6' lead wire and direct burial
gel filled wire nuts (12V) or
standard wire nuts (120V) included*

120V

*Integral Brightness Control
Adjustable beam angle*

Input	110V - 120VAC
Power	3W to 11.5W
Brightness	65 lm to 515 lm
Beam Angle	15° to 60°
CRI	85
Rated Life	45,000 hours

3000K *Pure White*
5032-30BZ | Bronze on Aluminum
5032-30BBR | Bronze on Brass

See pages 17-18 for *ilumenight™ color changing 3" Inground lights*

Accessories


Rock Guard		5030-GRD-BZ 5030-GRD-BBR	Bronze on Aluminum Bronze on Brass	Protects the fixture surface
Optics		LENS-25-AMB LENS-25-GRN LENS-25-RED LENS-25-BLU LENS-25-FR LENS-25-HCL	Amber Green Red Blue Frosted Honeycomb Louver Reduces glare	Enhances saturation of florals and foliage
Concrete Pour Kit		5030-PIP-PVC	Shown with temporary dense foam cap	For installation in concrete Five 1/2" NPT threaded holes, PC



- Color Changing
- App-controlled brightness
- IP66 rated (Accent, Wall Wash), IP67 rated (Inground)
- Solid Die-cast brass
- Factory sealed water tight fixtures
- 6' lead wire
- Constant output for 9V-15V input

ACCENT 12V COLOR CHANGING

Color and brightness controlled with ilumenight™ mobile app



Input 9-15VAC
 Power 0.5W to 14.5W / 1VA to 17VA
 Brightness Up to 355 lm
 Beam Angle 15° to 60°
 CRI 95+
 Rated Life 45,000 hours




Model	Finishes
5011-CCBBR	Bronze on Brass
5011-CCBZ	Bronze on Aluminum

See page 8 for accessories

WALL WASH 12V COLOR CHANGING

Color and brightness controlled with ilumenight™ mobile app



Input 9-15VAC
 Power 0.5W to 14.5W / 1VA to 17VA
 Brightness Up to 430 lm
 Beam Angle 15° upward (50° by 80°)
 CRI 95+
 Rated Life 45,000 hours




Model	Finishes
5021-CCBBR	Bronze on Brass

See page 12 for accessories

3" INGROUND 12V COLOR CHANGING

Color and brightness controlled with ilumenight™ mobile app



Input 9-15VAC
 Power 0.5W to 14.5W / 1VA to 17VA
 Brightness Up to 250 lm
 Beam Angle 15° to 60°
 CRI 95+
 Rated Life 45,000 hours



Model	Finishes
5031-CCBBR	Bronze on Brass

See page 16 for accessories

ilumenight LED LANDSCAPE


MAKE IT
COLORFUL!


With ilumenight™ you can take your landscape from warm white to pure white to cool white, red to violet and every color in between all with the touch of a finger.

STEP 1 Download Free "ilumenight™" app

STEP 2 Setup Login

STEP 3 Command all of your ilumenight landscape fixtures at will



- 
- Conveniently adapts into existing 12V system
 - Translucent diffuser eliminates worrisome hotspots for even light projection
 - Mounting options included: Stainless Steel Under Capstone Brackets, Clips and Hardware
 - Simple two screw mounting option into handrails, bench seats, decks, steps and fences
 - IP66 rated, protected against high pressure water jets
 - Potted electronics and conformal coated LEDs for long term moisture protection

HARDSCAPE LED LANDSCAPE



7181

Maximum lumen output and length make this a great fixture for large areas and where more light is needed.

18"



7121

Great for under deck hand rails in place of traditional deck lights or walls where more light is needed to evenly graze the wall surface.

12"



7061

Most popular size for masonry walls that are 40 inches tall or less. At 40 inches, spacing of 4 feet on center is recommended.






6"



7031

Perfect for those hard to access, short areas, columns, posts, walls and tight turns.

3"



Model *Color Temp* *Finishes*

18" HARDSCAPE

Input 9 - 15VAC
 Power 9.3W, 13.4VA
 Brightness Up to 265 lm
 CRI 90+
 Rated Life 70,000 hours

7181-27BZ
7181-30BZ

2700K Warm White
 3000K Pure White

Bronze on
 Aluminum

12" HARDSCAPE

Input 9 - 15VAC
 Power 6.5W, 10.1VA
 Brightness Up to 185 lm
 CRI 90+
 Rated Life 70,000 hours

7121-27BZ
7121-30BZ

2700K Warm White
 3000K Pure White

Bronze on
 Aluminum

6" HARDSCAPE

Input 9 - 15VAC
 Power 3.1W, 5.1VA
 Brightness Up to 90 lm
 CRI 90+
 Rated Life 70,000 hours

7061-27BZ
7061-30BZ

2700K Warm White
 3000K Pure White

Bronze on
 Aluminum

3" HARDSCAPE

Input 9 - 15VAC
 Power 1.4W, 2.5VA
 Brightness Up to 40 lm
 CRI 90+
 Rated Life 70,000 hours

7031-27BZ
7031-30BZ

2700K Warm White
 3000K Pure White

Bronze on
 Aluminum

12V OUTDOOR SUBMERSIBLE LANDSCAPE TAPE LIGHTING



- Submersible up to 5 feet
- May be tied into any 12V landscape lighting system
 - Maximum of 40 ft per run to stay within 5 amps
- Flexible linear lights maybe cut to desired length at the end of the run
- Various lengths may be joined together with IP68 rated connectors
 - UV-stabilized silicone seals and protects the tape sections

12V OUTDOOR SUBMERSIBLE LANDSCAPE TAPE LIGHTING




Integrates with other landscape lighting products using the same transformer



IP68 rated for submersion up to 5ft



Distinct mechanical and electrical connections minimizes spacing between LEDs when joining sections, and allows for seemingly endless tape runs that can be powered separately




		Model	Color Temp	Brightness
Input	12VAC			
Power	1.5W / 1.7VA per foot	8011	1 foot	
Brightness	Up to 115 lm per foot	8051	5 feet	27BK 2700K Warm White 110 lm per foot
CRI	85	8101	10 feet	30BK 3000K Pure White 115 lm per foot
Rated Life	60,000 hours			

Example: **8051-30BK**

Accessories

Clear channel		LED-TO24-CH5	5 feet Includes mounting hardware	Lead wire with 5A fuse		8000-06BK 6 feet 8000-10BK 10 feet	40 ft max tape run. Protects tape sections from over current
End cap		LED-TO24-EC		Joiner Cable - Short		8001-6BK 6 inch 8001-12BK 1 foot	
Surface mounting clip		LED-TO24-C1	Secures on both edges (10 Qty)	Joiner Cable - Long		8001-72BK 6 feet 8001-120BK 10 feet	
Edge mounting clip		LED-TO24-C2	Secures on one edge (10 Qty)	4 Way "X" Connector		8003-BK	
Invisible clip		LED-TO24-C3	Spring clip secures beneath tape (10 Qty)	3 Way "Y" Connector		8002-BK	



SUBMERSIBLE 2" LED LANDSCAPE

- Constant output for 9V-15V input
- 100%-10% dimming - see specification sheet for list of tested dimmers
- May be used in conjunction with all WAC Landscape Lighting products
- Includes a detachable stainless steel mounting bracket for use in or out of water

SUBMERSIBLE 2" LED LANDSCAPE

IP68



676 listed

- Solid Stainless Steel construction
- IP68 rated, Suitable for continuous immersion under water
- Factory sealed water tight fixtures
- 30' long lead wire




2031
ROUND

Included Stainless Steel easy mount accessory for use with underwater applications and above ground on any surface.



Designed for underwater or wet application.
30ft long lead wire.

Model



Input	9-15VAC
Power	4.1W / 6.6VA
Brightness	170 lm
Color Temp	3000 K
CRI	85
Beam Angle	25°
Rated Life	70,000 hours

2031-30SS

Stainless Steel

RECESSED INGROUNDS + INDICATOR LED LANDSCAPE




- IP68 rated, Suitable for continuous immersion under water
 - Factory sealed water tight fixtures
 - Solid stainless steel construction
- Options for use in outdoor downlight applications
 - Constant output for 9V-15V input
- 100%-10% dimming - see specification sheet for list of tested dimmers
- Available concrete pour kit with 18" PVC pipe which can be field shortened

RECESSED INGROUNDS + INDICATOR LED LANDSCAPE

2" APERTURE

Input 9-15VAC
 Power 4.1W / 6.6VA
 Brightness Up to 170 lm
 Color Temp 3000K Pure White

CRI 85
 Beam Angle 25°
 Rated Life 70,000 hours



				Model	Finishes
				2011-30SS 2011-30BS	Stainless Steel Bronzed Stainless Steel
				Slim Round with Honeycomb Louver	Stainless Steel Bronzed Stainless Steel
				2021-30SS 2021-30BS	Stainless Steel Bronzed Stainless Steel
				2 inch Round with Honeycomb Louver	Stainless Steel Bronzed Stainless Steel
				2051-30SS 2051-30BS	Stainless Steel Bronzed Stainless Steel
				2 inch Square with Honeycomb Louver	Stainless Steel Bronzed Stainless Steel


6' lead wire included

		2000-CON-PVC 2" Concrete Pour Kit	For installation in concrete. Use with a 4" outdoor rated junction box and 18" PVC pipe included.
--	--	---	---

1" APERTURE

Input 9-15VAC
 Power 1.9W 3VA
 Brightness 80 lm
 Color Temp 3000K Pure White

CRI 85
 Beam Angle 50°
 Rated Life 70,000 hours



				Model	Finishes
				1011-30SS	Stainless Steel
				1 inch Round	Stainless Steel
				1021-30SS	Stainless Steel
				1 inch Round with Honeycomb Louver	Stainless Steel
				1051-30SS	Stainless Steel
				1 inch Square with Honeycomb Louver	Stainless Steel

6' lead wire included



		1000-CON-PVC 1" CONCRETE POUR KIT	For installation in concrete. Use with a 4" outdoor rated junction box and 18" PVC pipe included.
--	--	---	---

2" RECESSED INGROUNDS + INDICATOR LED LANDSCAPE



- IP68 rated, Suitable for continuous immersion under water
 - Factory sealed water tight fixtures
 - Solid stainless steel construction
 - Constant output for 9V-15V input
- 10%-100% dimming - see specification sheet for list of tested dimmers
- Available concrete pour kit with 18" PVC pipe which can be field shortened

2" RECESSED INGROUNDS + INDICATOR LED LANDSCAPE




2" GROUND HOOD

Optional spring clip accessory included

Input 9-15VAC
 Power 4.1W / 6.6VA
 Brightness 25 lm
 Color Temp 3000K
 CRI 85
 Beam Angle Asymmetrical
 Rated Life 70,000 hours

2081-30SS Stainless Steel
2081-30BS Bronzed Stainless Steel




6' lead wire included



2000-CON-PVC
 2" Concrete Pour Kit

For installation in concrete. Use with a 4" outdoor rated junction box and 18" PVC pipe included.



Model Finishes

2" BI-DIRECTIONAL

Optional spring clip accessory included

Input 9-15VAC
 Power 4.1W / 6.6VA
 Brightness 5 lm
 Color Temp 3000K
 CRI 85
 Rated Life 70,000 hours

2071-30SS Stainless Steel
2071-30BS Bronzed Stainless Steel



6' lead wire included



2000-CON-PVC
 2" Concrete Pour Kit

For installation in concrete. Use with a 4" outdoor rated junction box and 18" PVC pipe included.




- IP66 rated, Protected against powerful water jets
- Translucent lens provides for uniform diffused light output
- 100%-10% dimming - see specification for list of tested dimmers
- Solid diecast brass or corrosion resistant aluminum alloy
 - ADA compliant



3031

Input 9 - 15VAC
 Power 2.8W 4.6VA
 Brightness 75 lm
 CRI 90+
 Rated Life 50,000 hours




Model	Color Temp	Finishes
3031	27 2700K Warm White	BK Black on Aluminum BBR Bronze on Brass BZ Bronze on Aluminum WT White on Aluminum
	30 3000K Cool White	

Example: 3031-30BZ



3011

Input 9 - 15VAC
 Power 2.8W 4.6VA
 Brightness 60 lm
 CRI 90+
 Rated Life 50,000 hours




Model	Color Temp	Finishes
3011	27 2700K Warm White	BK Black on Aluminum BBR Bronze on Brass BZ Bronze on Aluminum WT White on Aluminum
	30 3000K Cool White	

Example: 3011-27WT



3021

Input 9 - 15VAC
 Power 2.8W 4.6VA
 Brightness 60 lm
 CRI 90+
 Rated Life 50,000 hours



Model	Color Temp	Finishes
3021	27 2700K Warm White	BK Black on Aluminum BBR Bronze on Brass BZ Bronze on Aluminum WT White on Aluminum
	30 3000K Cool White	

Example: 3021-30BBR

STEP LIGHTS LED LANDSCAPE

- Invisible hardware
- IP66 rated, Protected against high-pressure water jets
- Constant output for 9V-15V input
- 100%-10% dimming



STEP LIGHTS LED LANDSCAPE







1838 listed (12V)
1598 listed (120V)

CIRCLE AND SQUARE STEP LIGHTS

- Solid stainless steel construction
- Includes a spring clip for wall or step applications
- 6' lead wire





Model

Circle		Square	
			
2 3/4"	1 7/8"	2 3/4"	1 7/8"
Circle 2041		Square 2061	
Input	9-15VAC	Input	9-15VAC
Power	4.1W / 6.6VA	Power	4.1W / 6.6VA
Brightness	50 lm	Brightness	50 lm
Color Temp	3000 K	Color Temp	3000 K
CRI	85	CRI	85
Rated Life	70,000 hours	Rated Life	70,000 hours
2041-30SS		2061-30SS	
	<i>Stainless Steel</i>		<i>Stainless Steel</i>
	<i>Bronzed Stainless Steel</i>		<i>Bronzed Stainless Steel</i>

RECTANGLE STEP LIGHTS

Solid Die-cast brass, corrosion resistant aluminum alloy, or cast stainless steel construction

	12V	120V
Input	9 - 15VAC	110 - 120VAC
Power	2W 3.1VA	3.5W
Brightness	Up to 38 lm	Up to 65 lm
CRI	90+	90+
Rated Life	60,000 hours	54,000 hours



Voltage	Model	Color Temp	Finishes
12V	4011-27	2700K	BBR Bronze on Brass
	4011-30	3000K	BZ Bronze on Aluminum
	4011-AM	Amber	BK Black on Aluminum
120V**	WL-LED100-C-	3000K	WT White on Aluminum
	WL-LED100-AM-	Amber	SS* Cast Stainless Steel

Example: 4011-30BZ

*Cast Stainless Steel finish is only available in 3000K and Amber Colors.

**Available in 277V; Example: WL-LED100F-C-WT


Voltage	Model	Color Temp	Finishes
12V	4021-27	2700K	BZ Bronze on Aluminum
	4021-30	3000K	BK Black on Aluminum
	4021-AM	Amber	WT White on Aluminum
120V**	WL-LED200-C-	3000K	SS* Cast Stainless Steel
	WL-LED200-AM-	Amber	

Example: 4021-AMBK


LEDGE LED PATH

- IP66 rated, Protected against high-pressure water jets
- Factory sealed water tight fixtures
- Constant output for 9V-15V input





- Sleek linear design blends seamlessly into pathways while providing soft, even illumination
- Recommended spacing for installation :
Residential: 8 to 10ft
Commercial: 5 to 7ft



		Model	Color Temp	Finishes
Input	9 - 15VAC	6081	27 2700K Warm White 30 3000K Pure White	BZ Bronze on Aluminum BK Black on Aluminum
Power	3.0W, 4.5VA			
Brightness	Up to 105 lm			
CRI	90			
Rated Life	60,000 hours			

Example: 6081-27BZ

Mounting stake, 6 foot lead wire, and direct burial gel filled wire nuts included

Accessories


Additional Mounting Stake		9000-ST9-BK	Bronze	Durable PC stake
Surface Mount Flange/Stake		5000-SCP-BZ	Bronze on Aluminum	Includes three 7 inch threaded stainless steel stabilizing pins for ground mounting or surface mounts with four screws or over a junction box
Guardian Mount		9000-SP9-BZ	Stainless Steel	Heavy duty stainless steel spike to position fixture Formed from a single piece of metal

SLIDE LED PATH


- IP66 rated, Protected against high-pressure water jets
- Factory sealed water tight fixtures
- Constant output for 9V-15V input



SLIDE LED PATH



6321





6311

- Sleek linear design blends seamlessly into pathways while providing soft, even illumination
- Recommended spacing for installation :

6321 Large
Residential: 9 to 11ft
Commercial: 5 to 7ft

6311 Small
Residential: 7 to 9ft
Commercial: 4 to 6ft



	Model	Color Temp	Finishes
Input	9 - 15VAC		
Power	3.0W, 4.5VA		
Brightness	Up to 95 lm		
CRI	90		
Rated Life	60,000 hours		
	6311	30	BZ
	Small	3000K Pure White	Bronze on Aluminum
Input	9 - 15VAC		
Power	3.0W, 4.5VA		
Brightness	Up to 95 lm		
CRI	90		
Rated Life	60,000 hours		
	6321		
	Large		

Example: 6311-30BZ

Mounting stake, 6 foot lead wire, and direct burial gel filled wire nuts included

Accessories



Additional Mounting Stake		9000-ST9-BK	Bronze	Durable PC stake
Surface Mount Flange/Stake		5000-SCP-BZ	Bronze on Aluminum	Includes three 7 inch threaded stainless steel stabilizing pins for ground mounting or surface mounts with four screws or over a junction box
Guardian Mount		9000-SP9-BZ	Stainless Steel	Heavy duty stainless steel spike to position fixture Formed from a single piece of metal

LINEAR LED PATH


- IP66 rated, Protected against high-pressure water jets
- Factory sealed water tight fixtures
- Constant output for 9V-15V input



LINEAR LED PATH



- Sleek linear design blends seamlessly into pathways while providing soft, even illumination
- Recommended spacing for installation :
Residential: 7 to 9ft
Commercial: 4 to 6ft



		Model	Color Temp	Finishes
Input	9 - 15VAC	6021	27 2700K Warm White 30 3000K Pure White	BZ Bronze on Aluminum BK Black on Aluminum
Power	2.9W, 4.7VA			
Brightness	Up to 95 lm			
CRI	90			
Rated Life	60,000 hours			

Example: 6021-30BK

Mounting stake, 6 foot lead wire, and direct burial gel filled wire nuts included


Accessories

Additional Mounting Stake		9000-ST9-BK	Bronze	Durable PC stake
Surface Mount Flange/Stake		5000-SCP-BZ	Bronze on Aluminum	Includes three 7 inch threaded stainless steel stabilizing pins for ground mounting or surface mounts with four screws or over a junction box
Guardian Mount		9000-SP9-BZ	Stainless Steel	Heavy duty stainless steel spike to position fixture Formed from a single piece of metal


BALANCE SINGLE LED PATH

- IP66 rated, Protected against high-pressure water jets
- Factory sealed water tight fixtures
- Constant output for 9V-15V input





- Sleek linear design blends seamlessly into pathways while providing soft, even illumination
- Recommended spacing for installation :
Residential: 11 to 13ft
Commercial: 7 to 9ft



		Model	Color Temp	Finishes
Input	9 - 15VAC	6061	27 2700K Warm White 30 3000K Pure White	BZ Bronze on Aluminum BK Black on Aluminum
Power	6.5W, 11.5VA			
Brightness	Up to 275 lm			
CRI	90			
Rated Life	60,000 hours			

Example: 6061-30BZ

Mounting stake, 6 foot lead wire, and direct burial gel filled wire nuts included


Accessories

Additional Mounting Stake		9000-ST9-BK	Bronze	Durable PC stake
Surface Mount Flange/Stake		5000-SCP-BZ	Bronze on Aluminum	Includes three 7 inch threaded stainless steel stabilizing pins for ground mounting or surface mounts with four screws or over a junction box
Guardian Mount		9000-SP9-BZ	Stainless Steel	Heavy duty stainless steel spike to position fixture Formed from a single piece of metal


BALANCE DOUBLE LED PATH

- IP66 rated, Protected against high-pressure water jets
 - Factory sealed water tight fixtures
 - Constant output for 9V-15V input





- Sleek linear design blends seamlessly into pathways while providing soft, even illumination
- Recommended spacing for installation :
Residential: 11 to 13ft
Commercial: 7 to 9ft



		Model	Color Temp	Finishes
Input	9 - 15VAC	6071	27 2700K Warm White 30 3000K Pure White	BZ Bronze on Aluminum BK Black on Aluminum
Power	10.0W, 14VA			
Brightness	Up to 375 lm			
CRI	90			
Rated Life	60,000 hours			

Example: 6071-30BZ


Mounting stake, 6 foot lead wire, and direct burial gel filled wire nuts included

Accessories


Additional Mounting Stake		9000-ST9-BK	Bronze	Durable PC stake
Surface Mount Flange/Stake		5000-SCP-BZ	Bronze on Aluminum	Includes three 7 inch threaded stainless steel stabilizing pins for ground mounting or surface mounts with four screws or over a junction box
Guardian Mount		9000-SP9-BZ	Stainless Steel	Heavy duty stainless steel spike to position fixture Formed from a single piece of metal



- IP66 rated, Protected against high-pressure water jets
- Factory sealed water tight fixtures
- Constant output for 9V-15V input






- Sleek linear design blends seamlessly into pathways while providing soft, even illumination
- Recommended spacing for installation :
Residential: 8 to 10ft
Commercial: 5 to 7ft

		Model	Color Temp	Finishes
Input	9 - 15VAC	6091	27 2700K Warm White 30 3000K Pure White	BZ Bronze on Aluminum 
Power	3.0W, 4.5VA			
Brightness	Up to 100 lm			
CRI	90			
Rated Life	60,000 hours			

Example: 6091-27BZ


Mounting stake, 6 foot lead wire, and direct burial gel filled wire nuts included

Accessories


Additional Mounting Stake		9000-ST9-BK	Bronze	Durable PC stake
Surface Mount Flange/Stake		5000-SCP-BZ	Bronze on Aluminum	Includes three 7 inch threaded stainless steel stabilizing pins for ground mounting or surface mounts with four screws or over a junction box
Guardian Mount		9000-SP9-BZ	Stainless Steel	Heavy duty stainless steel spike to position fixture Formed from a single piece of metal

ECLIPSE LED PATH

- IP66 rated, Protected against high-pressure water jets
 - Factory sealed water tight fixtures
 - Solid diecast corrosion resistant aluminum alloy
 - Constant output for 9V-15V input



- Sturdy side mount design works well in applications where directional illumination is desired
- Recommended spacing for installation :
Residential: 8 to 10ft
Commercial: 5 to 7ft






		Model	Color Temp	Finishes	
Input	9 - 15VAC	6031	27 2700K Warm White 30 3000K Pure White	BBR	Bronze on Brass* 
Power	2.9W / 4.7VA			BZ	Bronze on Aluminum 
Brightness	Up to 125 lm			BK	Black on Aluminum 
CRI	90				
Rated Life	60,000 hours				

Example: 6031-30BZ

6 foot lead wire, and direct burial gel filled wire nuts included

*Guardian mount accessory included in Bronze on Brass; Mounting stake accessory included in Bronze and Black on Aluminum



Accessories

Additional Mounting Stake		9000-ST9-BK	Bronze	Durable PC stake
Surface Mount Flange/Stake		5000-SCP-BZ 5000-SCP-BBR	Bronze on Aluminum Bronze on Brass	Includes three 7 inch threaded stainless steel stabilizing pins for ground mounting or surface mounts with four screws or over a junction box
Guardian Mount		9000-SP9-BZ	Stainless Steel	Heavy duty stainless steel spike to position fixture Formed from a single piece of metal

AREA LED AREA LIGHT



- IP66 rated, Protected against high-pressure water jets
 - Factory sealed water tight fixtures
- Solid brass or corrosion resistant aluminum alloy
 - Constant output for 9V-15V input



- Broad appeal makes this fixture suitable for varying landscape designs
- Recommended spacing for installation :
Residential: 11 to 13ft
Commercial: 7 to 9ft

		Model	Color Temp	Finishes
Input	9 - 15VAC	6011	27 2700K Warm White 30 3000K Pure White	BBR Bronze on Brass BZ Bronze on Aluminum BK Black on Aluminum
Power	5.8W / 9.4VA			
Brightness	Up to 150 lm			
CRI	90			
Rated Life	60,000 hours			

Example: 6011-30BK

Mounting stake, 6 foot lead wire, and direct burial gel filled wire nuts included



Accessories

Additional Mounting Stake		9000-ST9-BK	Bronze	Durable PC stake
Surface Mount Flange/Stake		5000-SCP-BZ 5000-SCP-BBR	Bronze on Aluminum Bronze on Brass	Includes three 7 inch threaded stainless steel stabilizing pins for ground mounting or surface mounts with four screws or over a junction box
Guardian Mount		9000-SP9-BZ	Stainless Steel	Heavy duty stainless steel spike to position fixture Formed from a single piece of metal

TIKI LED AREA LIGHT

- IP66 rated, Protected against high-pressure water jets
- Factory sealed water tight fixtures
- Solid brass or corrosion resistant aluminum alloy
- Constant output for 9V-15V input





- Sturdy side mount design works well in applications where directional illumination is desired
- Recommended spacing for installation :
Residential: 7 to 9ft
Commercial: 5 to 7ft

		Model	Color Temp	Finishes
Input	9 - 15VAC	6041	27 2700K Warm White 30 3000K Pure White	BBR Bronze on Brass BZ Bronze on Aluminum BK Black on Aluminum
Power	6.5W, 9.5VA			
Brightness	Up to 225 lm			
CRI	90			
Rated Life	60,000 hours			

Example: 6041-30BK

Mounting stake, 6 foot lead wire, and direct burial gel filled wire nuts included

Accessories



Additional Mounting Stake		9000-ST9-BK	Bronze	Durable PC stake
Surface Mount Flange/Stake		5000-SCP-BZ 5000-SCP-BBR	Bronze on Aluminum Bronze on Brass	Includes three 7 inch threaded stainless steel stabilizing pins for ground mounting or surface mounts with four screws or over a junction box
Guardian Mount		9000-SP9-BZ	Stainless Steel	Heavy duty stainless steel spike to position fixture Formed from a single piece of metal

CANOPY LED AREA LIGHT

- IP66 rated, Protected against high-pressure water jets
 - Factory sealed water tight fixtures
- Solid brass or corrosion resistant aluminum alloy
 - Constant output for 9V-15V input



CANOPY LED AREA LIGHT



- Sturdy side mount design works well in applications where directional illumination is desired
- Recommended spacing for installation :
Residential: 7 to 9ft
Commercial: 5 to 7ft

		Model	Color Temp	Finishes
Input	9 - 15VAC	6051	27 2700K Warm White 30 3000K Pure White	BBR Bronze on Brass BZ Bronze on Aluminum BK Black on Aluminum
Power	6.5W, 9.5VA			
Brightness	Up to 225 lm			
CRI	90			
Rated Life	60,000 hours			

Example: 6051-30BBR

Mounting stake, 6 foot lead wire, and direct burial gel filled wire nuts included

Accessories

Additional Mounting Stake		9000-ST9-BK	Bronze	Durable PC stake
Surface Mount Flange/Stake		5000-SCP-BZ 5000-SCP-BBR	Bronze on Aluminum Bronze on Brass	Includes three 7 inch threaded stainless steel stabilizing pins for ground mounting or surface mounts with four screws or over a junction box
Guardian Mount		9000-SP9-BZ	Stainless Steel	Heavy duty stainless steel spike to position fixture Formed from a single piece of metal

MINI ACCENT LED PATH

- Includes 6", 12" and 24" extensions
- IP66 rated, Protected against high-pressure water jets
 - 10° - 50° beam adjustability
- Continuously adjustable beam angles and brightness control
 - Detachable shroud
- Constant output for 9V-15V input




MINI ACCENT LED PATH



IP66



1838 listed (12V)



6111



6211

		Model	Color Temp	Finishes	
Input	9-15VAC	6111 Single	27 2700K Warm White	BZ Bronze on Aluminum	
Power	1W to 7W/ 2VA-10.5VA				
Brightness	45lm to 365lm				
CRI	85				
Rated Life	70,000 hours				
Input	9-15VAC	6211 Double	30 3000K Pure White	BBR Bronze on Bronze	
Power	1W to 7W/ 2VA-10.5VA x 2				
Brightness	45lm to 365lm x 2				
CRI	85				
Rated Life	70,000 hours				

Example: 6111-30BZ

Guardian mount, 6 foot lead wire, and direct burial gel filled wire nuts included

Accessories

5" Long Shroud		5111-LSHR-BZ 5111-LSHR-BBR	Bronze on Aluminum Bronze on Brass	Reduce glare. Ideal for downlighting application
Surface Mount Flange/Stake		5000-SCP-BZ 5000-SCP-BBR	Bronze on Aluminum	Includes three 7 inch threaded stainless steel stabilizing pins for ground mounting or surface mounts with four screws or over a junction box
Additional Guardian Mount		9000-SP9-BZ	Stainless Steel	Heavy duty stainless steel spike to position fixture Formed from a single piece of metal

GATE LED BOLLARD/PATH

- IP66 rated, Protected against high-pressure water jets
- Factory sealed water tight fixtures
- Constant output for 9V-15V input
- Mounting accessories included
- Detachable back plate for lighting control included



GATE LED BOLLARD/PATH

IP66

UL US 1838 listed (12V)



Shown without plate



Shown with plate



- Sleek linear design blends seamlessly into pathways while providing soft, even illumination

	<i>Model</i>	<i>Color Temp</i>	<i>Finishes</i>
Input	9 - 15VAC		
Power	7W, 7.5VA		
Brightness	Up to 115 lm	27 2700K Warm White	BZ Bronze on Aluminum
CRI	90	30 3000K Pure White	BK Black on Aluminum
Rated Life	60,000 hours		

Example: 6651-30BK

Mounting stake, 6ft lead wire and detachable back plate included

SCOOP 12V/120V/277V LED BOLLARD

- IP66 rated, Protected against high-pressure water jets
- Factory sealed water tight fixtures
- Constant output for 9V-15V input
- Mounting accessories included




SCOOP 12V/120V/277V LED BOLLARD

IP66



1838 listed (12V)
1598 listed (120V/277V)



- Sleek linear design blends seamlessly into pathways while providing soft, even illumination

		Model	Color Temp	Finishes
Input	9 - 15VAC	6611 12V	27 2700K Warm White 30 3000K Pure White	BZ Bronze on Aluminum BK Black on Aluminum
Power	5.7W, 6.0VA			
Brightness	Up to 135 lm			
CRI	90			
Rated Life	60,000 hours			
MLV dimming only				
Input	120V	6612 120V	27 2700K Warm White 30 3000K Pure White	BZ Bronze on Aluminum BK Black on Aluminum
Power	12.5W			
Brightness	Up to 350 lm			
CRI	90			
Rated Life	60,000 hours			
TRIAC or ELV dimming				
Input	277VAC	6613 277V	27 2700K Warm White 30 3000K Pure White	BZ Bronze on Aluminum BK Black on Aluminum
Power	10.5W			
Brightness	Up to 300 lm			
CRI	90			
Rated Life	60,000 hours			
ELV dimming only				

Example: 6611-30BZ
Mounting accessories included

CHAMBER 12V/120V/277V LED BOLLARD

- IP66 rated, Protected against high-pressure water jets
- Factory sealed water tight fixtures
- Constant output for 9V-15V input
- Mounting accessories included




CHAMBER 12V/120V/277V LED BOLLARD

IP66



1838 listed (12V)
1598 listed (120V/277V)



Mounting accessory included

M6000-STAKE

12V

120V/277V



- Sleek linear design blends seamlessly into pathways while providing soft, even illumination

		Model	Color Temp	Finishes
Input	9 - 15VAC	6631 12V	27 2700K Warm White 30 3000K Pure White	BZ Bronze on Aluminum BK Black on Aluminum
Power	5.5W, 6.0VA			
Brightness	Up to 140 lm			
CRI	90			
Rated Life	60,000 hours			
MLV dimming only				
Input	120V	6632 120V	27 2700K Warm White 30 3000K Pure White	BZ Bronze on Aluminum BK Black on Aluminum
Power	12.5W			
Brightness	Up to 360 lm			
CRI	90			
Rated Life	60,000 hours			
TRIAC or ELV dimming				
Input	277VAC	6633 277V	27 2700K Warm White 30 3000K Pure White	BZ Bronze on Aluminum BK Black on Aluminum
Power	10.5W			
Brightness	Up to 400 lm			
CRI	90			
Rated Life	60,000 hours			
ELV dimming only				

Example: 6633-30BZ

Mounting accessories included

TOWER 12V/120V/277V LED BOLLARD

- IP66 rated, Protected against high-pressure water jets
 - Factory sealed water tight fixtures
 - Constant output for 9V-15V input
 - Mounting accessories included




TOWER 12V/120V/277V LED BOLLARD

IP66



1838 listed (12V)
1598 listed (120V/277V)



- Sleek linear design blends seamlessly into pathways while providing soft, even illumination

	<i>Model</i>	<i>Color Temp</i>	<i>Finishes</i>
Input 9 - 15VAC Power 5.5W, 6.0VA Brightness Up to 185 lm CRI 90 Rated Life 60,000 hours MLV dimming only	6621 12V	27 2700K Warm White 30 3000K Pure White	BZ Bronze on Aluminum BK Black on Aluminum
Input 120V Power 12.5W Brightness Up to 455 lm CRI 90 Rated Life 60,000 hours TRIAC or ELV dimming	6622 120V	27 2700K Warm White 30 3000K Pure White	BZ Bronze on Aluminum BK Black on Aluminum
Input 277VAC Power 10.5W Brightness Up to 455 lm CRI 90 Rated Life 60,000 hours ELV dimming only	6623 277V	27 2700K Warm White 30 3000K Pure White	BZ Bronze on Aluminum BK Black on Aluminum

Example: 6622-30BZ
Mounting accessories included

PARK 12V/120V/277V LED BOLLARD

- IP66 rated, Protected against high-pressure water jets
- Factory sealed water tight fixtures
- Constant output for 9V-15V input
- Mounting accessories included




PARK 12V/120V/277V LED BOLLARD

IP66



1838 listed (12V)
1598 listed (120V/277V)




- Sleek linear design blends seamlessly into pathways while providing soft, even illumination

		Model	Color Temp	Finishes		
Input	9 - 15VAC	6641 12V	27 2700K Warm White 30 3000K Pure White	BZ Bronze on Aluminum		
Power	5.5W, 6.0VA				BK Black on Aluminum	
Brightness	Up to 150 lm					
CRI	90					
Rated Life	60,000 hours					
MLV dimming only						
Input	120V	6642 120V	27 2700K Warm White 30 3000K Pure White	BZ Bronze on Aluminum		
Power	12.5W				BK Black on Aluminum	
Brightness	Up to 390 lm					
CRI	90					
Rated Life	60,000 hours					
TRIAC or ELV dimming						
Input	277VAC	6643 277V	27 2700K Warm White 30 3000K Pure White	BZ Bronze on Aluminum		
Power	10.5W				BK Black on Aluminum	
Brightness	Up to 430 lm					
CRI	90					
Rated Life	60,000 hours					
ELV dimming only						

Example: 6641-30BZ
Mounting accessories included

LANDSCAPE LIGHTING DESIGN

2" SUBMERSIBLE



Step 1: Design

Select the focal points in the yard - these will be the main viewing objects on the projects and the first level of light. After determining how these focal points will be illuminated, you will fill in light to accent the other areas of the yard.

Step 2: Fixture Selection

Path and Area: Ideal for illuminating pathways or illuminating flower beds.

Accent: Use to create dramatic effects when up lighting or subtle moods when used for down lighting.

Wall Wash: Use to create an even wide flood of light on any surface.

Hardscape Fixtures: Perfect for under a stack stone wall, deck handrails or a bench seating.

Tape Lighting: Illuminate irregular shaped hardscapes, in or around water features and ponds, or in an outdoor kitchen for entertaining.

Submersible: Highlights ponds, water features and backyard streams.

Step/Deck/Patio/Indicator: Illuminate outdoor entertainment areas where foot traffic is prevalent

Step 3: Fixture Spacing:

Spacing is subjective. 6 feet of lead wire is provided across the offering for final location adjustments in the field

Bollard/ Path / Area: around 10' distance between each

Accents/Inground: Small objects require 1-2 fixtures, while large canopy trees with multiple viewing angles may require up to 4 fixtures.

Wall Wash: Placing 2' from your wall will cast nice even illumination

Hardscape: 3" for short, tight areas. 6" to illuminate under deck hand rails, retaining walls, or steps.

Larger sizes are available for greater illumination into areas needing a greater amount of light.

Tape Lighting: Tape lighting has approximately 40' maximum run distance, 5 amp max per run. Available in 1', 5' & 10' connectable lengths.

Indicator: Mark pathway borders with 18" spacing

Submersible: Rated for use up to 5 feet deep.


Step 4: Wire Runs

It is very likely that you will have several runs going out from the transformer to connect all of the fixtures. Adhere to transformer guidelines and above 9V at the end of the run. See waandscapelighting.com for wire sizing guide and further installation assistance.

Step 5: Transformer Sizing

Based on the fixture runs and number of fixtures on your project, you will select your transformer size (75W, 150W, 300W, 600W etc.).

TRANSFORMER LED LANDSCAPE



- IP65 Rated
- 12V to 15V taps
- Knock outs for power and photosensor connections
- 3-prong outlet for timer
- Outdoor rated stainless steel transformer contains an outdoor rated 3-prong plug for power



Model	
9075-TRN-SS	75W Max Dimensions: 13.97" L x 5.35"W x 5.63"H
9150-TRN-SS	150W Max Dimensions: 18.90" L x 6.69"W x 6.30"H
9300-TRN-SS	300W Max Dimensions: 18.90" L x 6.69"W x 6.30"H
9600-TRN-SS	600W Max (2 x 300W outputs) Dimensions: 14.49" L x 10.08"W x 5.94"H

ACCESSORIES LED LANDSCAPE

Mechanical Timer		9000-MTI-WT	White	Connect within the transformer
Photosensor		9000-PCH-GY	1000VA Max	Attached directly to the transformer
Photosensor - Remote		9000-PCR-GY	1000VA Max	If transformer is located in a shady spot, this photosensor has a 10 foot cord and a stainless steel bracket to secure in a sunny area
Direct Burial Water proof Wire Nuts		9020-WNT-BK		Silicone filled wire nut with gasket (Pack of 20pcs)
12V Direct Burial Outdoor Cable		9100-12G-BK 9250-12G-BK 9500-12G-BK	100 feet 12 gauge 250 feet 12 gauge 500 feet 12 gauge	

MOUNTING & GLARE CONTROL ACCESSORIES LED LANDSCAPE



6" Long Shroud For 5011/5012 Accent		5010-LSHR-BZ 5010-LSHR-BBR	Reduce glare. Ideal for downlighting application
5" Long Shroud For 5111 Accent		5111-LSHR-BZ 5111-LSHR-BBR	Reduce glare. Ideal for downlighting application
Tree Mount Junction Box		5000-TCP-BZ	Bronze on Aluminum box with Stainless steel mounting screws. Two 1/2" NPT threaded holes
Surface Mount Flange/Stake		5000-SCP-BZ 5000-SCP-BBR	Includes three 7 inch threaded stainless steel stabilizing pins for ground mounting or surface mounts with four screws or over a junction box
Guardian Mount		9000-SP9-BZ	Heavy duty stainless steel spike to position fixture. Formed from a single piece of metal
Gutter Mount Bracket		5000-GM-BZ	Stainless Steel universal mounting bracket for gutter mounting fixture





The 120V Crew

Line Voltage functional outdoor products have historically been gigantic.

LEDs can do the same job and eliminate the need for bulky fixture housings.

Older systems may now be easily updated for both commercial and residential spaces.

LED LANDSCAPE

 1598 listed


ACCENT 120V

Integral Brightness Control, Adjustable beam angle



Power 3.5W to 14.5W
Brightness 100lm to 900lm
Beam Angle 15° to 60°
CRI 85
Color Temp 3000K Pure White
Rated Life 45,000 hours
Listing IP-66

*Detachable shroud
 6' lead wire and wire nuts included*



Model **Finishes**

5012-30BZ Bronze on Aluminum
5012-30BRR Bronze on Brass


WALL WASH 120V

Integral Brightness Control



Power 3.5W to 14.5W
Brightness 95lm to 855lm
Beam Angle 15° upward (50° by 80°)
CRI 85
Color Temp 3000K Pure White
Rated Life 45,000 hours
Listing IP-66

6' lead wire and wire nuts included



Model **Finishes**

5022-30BZ Bronze on Aluminum
5022-30BRR Bronze on Brass

3" INGROUND 120V

Integral Brightness Control, Adjustable beam angle



Power 3W to 11.5W
Brightness 65lm to 515lm
Beam Angle 15° to 60°
CRI 85
Color Temp 3000K Pure White
Rated Life 45,000 hours
Listing IP-67

6' lead wire and wire nuts included



Model **Finishes**

5032-30BZ Bronze on Aluminum
5032-30BRR Bronze on Brass

BOLLARDS 120V-277V



Scoop
See pages 57-58



Chamber
See pages 59-60



Tower
See pages 61-62



Park
See pages 63-64




SHINING FROM THE BACKGROUND

Like professional stagehands, these high-performers easily disappear into the backdrop with their diminutive sizes while adaptably making the whole show possible

Featuring product: **5012-30BZ** Accent



24V OUTDOOR SUBMERSIBLE OUTDOOR TAPE LIGHTING



24V OUTDOOR SUBMERSIBLE OUTDOOR TAPE LIGHTING




Minimal spacing of LEDs when joined together



Actual Size

- Power:** 3.5W/ft
- Lumens:** up to 220 lm/ft
- CRI:** 90
- Rated Life:** 80,000 hours
- IP-68 rated, UL listed for wet location
- May be field cut every 6 inches at the end of a run
- Maximum run length of 28ft per electrical feed





Double insulated PVC encasement and distinct electrical and mechanical junctions allow for seemingly endless runs that can be powered separately

TAPE SELECTIONS

System	Color Temp	Length	Color
LED-TO2427	2700K	1 1 foot	WT White
LED-TO2430	3000K	5 5 feet	
LED-TO2435	3500K	10 10 feet	

Example: **LED-TO2435-10-WT**




CLASS 2 POWER SUPPLY FOR PRO OUTDOOR (REQUIRED)

Type	Model	Power	Input	Output	Dimmable	
Remote Damp Location	 EN-OD24100-RB2-T	96W	120V AC	24V AC	ELV	Includes a 6 foot lead wire
Remote Wet Location	 EN-O24100-RB2-T	96W	120V - 277V AC	24V DC	0-10V	Includes a 6 foot lead wire





Clear Channel	LED-TO24-CH5	5 feet
---------------	---------------------	--------



Includes a diffuser, two end caps, and five screws
Snap in to hold outdoor InvisiLED tape

	Type 1 Clip Secures on both edges	LED-TO24-C1	10 pcs 20 Screws
	Type 2 Clip Secures on one edge	LED-TO24-C2	10 pcs 10 Screws
	Type 3 Clip Holds from the underside	LED-TO24-C3	10 pcs 10 Screws

Clips to hold indoor InvisiLED tapes
For Pro Outdoor, Palette Outdoor, or Landscape Tape Light

	3-Way "Y" Connector Connects tape sections	LED-TO24-Y
	4-Way "X" Connector Connects tape sections	LED-TO24-X

Compatible with Pro Outdoor, Landscape Tape Light

	Joiner Cable Extends distance between transformers and controllers	LED-TO24-IC6 LED-TO24-IC12 LED-TO24-IC72 LED-TO24-IC120	6 in 12 in 72 in 120 in
	End cap 1 cut and 1 male end cap	LED-TO24-EC	Black


Compatible with Pro Outdoor, Palette Outdoor, Landscape Tape Light

24V OUTDOOR SUBMERSIBLE OUTDOOR TAPE LIGHTING



1838 listed

Minimal spacing of LEDs when joined together




Power: 1.5W / ft
Lumens: 40 lm/ft on
 3500K setting
Rated Life: 80,000 hours

- IP-68 rated, UL listed for wet location
- Variable colors with 3500K White
- DMX and wireless controller options for Palette outdoor system
- Maximum run length of 40 feet
- May be field cut every 2 inches at the end of a run
- Dim with wired controller and wireless controller accessory



Double insulated PVC encasement and distinct electrical and mechanical junctions allow for seemingly endless runs that can be powered separately



TAPE SELECTION

System	Length	Type
LED-TCO	1 1 foot	RGB Color Changing
	5 5 feet	
	10 10 feet	

Example: **LED-TCO-5-RGB**

CONTROLLER FOR PALETTE OUTDOOR (REQUIRED)

Master Controller (required)		LED-TO24-CM	4 function wired controller
Wireless Controller (required)		LED-TO24-WS	4 function wireless controller
Slave Controller (optional)		LED-TO24-CS	Connects to Master Controller, adding 40 ft run Compatible with Palette Outdoor

CLASS 2 POWER SUPPLY FOR PALETTE OUTDOOR (REQUIRED)

Type	Model	Power	Input	Output
Remote Wet Location	 EN-O24100-RB2-T	96W	120V - 277V AC	24V DC Includes a 6 foot lead wire

ACCESSORIES FOR PALETTE OUTDOOR

	Signal Wire Master to Slave controller or Slave to Slave	LED-TO24-SW60 LED-TO24-SW120	60 in 120 in
	DMX Signal Wire DMX to Master controller	LED-TO24-MW60 LED-TO24-MW120	60 in 120 in
	RGB Joiner Cable Extends distance between tape and to controllers	LED-TO24-IC6-RGB LED-TO24-IC12-RGB LED-TO24-IC72-RGB LED-TO24-IC120-RGB	6 in 12 in 72 in 120 in


	3-Way "Y" Connector Connects tape sections	LED-TO24-Y-RGB
	4 Way "X" Connector Connects tape sections	LED-TO24-X-RGB

Compatible with Palette Outdoor


24V OUTDOOR SUBMERSIBLE OUTDOOR TAPE LIGHTING






Featured Product: **LED-TCO-5-RGB** with **LED-TO24-CH5**

	Clear Channel	LED-TO24-CH5	5 feet
---	----------------------	---------------------	--------

Includes a diffuser, two end caps, and five screws
 Pro Outdoor, Palette Outdoor, Landscape Tape Light
 Snap in to hold outdoor InvisiLED tape

	End cap	LED-TO24-EC	Black
---	----------------	--------------------	-------

1 cut and 1 male end cap
 Compatible with Pro Outdoor, Palette Outdoor, Landscape Tape Light

	Type 1 Clip	LED-TO24-C1	10 pcs 20 Screws
	Type 2 Clip	LED-TO24-C2	10 pcs 10 Screws
	Type 3 Clip	LED-TO24-C3	10 pcs 10 Screws

Clips to hold indoor InvisiLED tapes
 Pro Outdoor, Palette Outdoor, Landscape Tape Light





WL-5105

Opal

Input: 120V
CRI: 90
Dimming: 100% - 10% ELV
Rated Life: 80,000 hours

WL-5205

Louver

Input: 120V
CRI: 90
Dimming: 100% - 10% ELV
Rated Life: 80,000 hours



- Factory-Sealed LED Light Engine
- Die-cast Aluminum Construction
- 120V Direct Wire - No Driver Needed
- Easily retrofit most existing incandescent brick light installations with this maintenance free LED upgrade


			<i>Max</i> <i>Delivered</i> <i>Power</i>	<i>Color</i> <i>Lumens</i>	<i>Temp</i>	<i>Finish</i>
		WL-5105-30 <i>Opal</i>	5.5W	110	3000K	ABZ <i>Architectural Bronze</i>
						ABK <i>Architectural Black</i>
<hr/>						
		WL-5205-30 <i>Louver</i>	5.5W	45	3000K	ABZ <i>Architectural Bronze</i>
						ABK <i>Architectural Black</i>
<hr/>						
AGH <i>Architectural Graphite</i>						
AWT <i>Architectural White</i>						

Example: WL-5105-30-aWT



Endurance™ LED FLOOD LIGHTS

FLOOD



Input: 120V
CRI: 85
Dimming: 100% - 10% ELV
Rated Life: 50,000 hours

- Waterproof breathable technology to maintain stable atmospheric pressure free from condensation
- Factory-Sealed LED Light Engine
- Die-cast Aluminum Construction
- 120V Direct Wire - No Driver Needed
- 1/2" Threaded Heavy Duty Mounting Arm
- Photo/Motion Sensor Sold Separately


	Power	Comparable	Color Temp	Delivered Lumens	Finish
	WP-LED335	35.5W	100W HID	30 3000K	ABZ Architectural Bronze AGH Architectural Graphite AWT Architectural White
				50 5000K	

Example: WP-LED335-30-AWT

MOTION SENSOR (120V) available in 3 complementary colors



PHOTOSENSOR (120V) available in 3 complementary colors



Endurance™ LED FLOOD LIGHTS

SINGLE SPOT



Input: 120V
CRI: 85
Dimming: 100% - 10% ELV
Rated Life: 39,000 hours

- Factory-sealed LED light engine
- Die-cast aluminum construction
- 120V direct wire - no driver needed
- Photo/motion sensor sold separately

	Power	Comparable	Color Temp	Delivered Lumens	Finish
	15W	75W Halogen	30 3000K 50 5000K	965 1030	ABZ Architectural Bronze AGH Architectural Graphite AWT Architectural White

Example: WP-LED415-30-AWT

MOTION SENSOR (120V) available in 3 complementary colors

	MS-120-BZ Bronze	
	MS-120-GY Gray	
	MS-120-WT White	

PHOTOSENSOR (120V) available in 3 complementary colors

	PC-120-BZ Bronze	
	PC-120-GY Gray	
	PC-120-WT White	

Endurance™ LED FLOOD LIGHTS

DOUBLE SPOT



Input: 120V
CRI: 85
Dimming: 100% - 10% ELV
Rated Life: 39,000 hours

- Factory-sealed LED light engine
- Die-cast aluminum construction
- 120V direct wire - no driver needed
- Photo/motion sensor sold separately

	Power	Comparable	Color Temp	Delivered Lumens	Finish
<p>WP-LED430</p>	30W	2 x 75W Halogen	30 3000K 50 5000K	965 x2 1030 x2	ABZ Architectural Bronze AGH Architectural Graphite AWT Architectural White

Example: WP-LED430-30-ABZ

MOTION SENSOR (120V) available in 3 complementary colors

	MS-120-BZ	Bronze	
	MS-120-GY	Gray	
	MS-120-WT	White	

PHOTOSENSOR (120V) available in 3 complementary colors

	PC-120-BZ	Bronze	
	PC-120-GY	Gray	
	PC-120-WT	White	

Endurance™ LED ADJUSTABLE FLOOD LIGHT


Safety cable recommended for extensions over 36"

Rotate to continuously adjust beam angles indexed at 15°, 25°, 40°, 60°

Detachable Shroud

Rotate 180°

Extendable rod



Comes with extension rod kit to extend up to 48" total

SINGLE
WP-LED514

CRI: 85
Rated Life: 50,000 hours
Dimming: 100% - 10% ELV
Input: 120V

DOUBLE
WP-LED529

CRI: 85
Rated Life: 50,000 hours
Dimming: 100% - 10% ELV
Input: 120V

- Factory-Sealed LED Light Engine
- Die-cast Aluminum Construction
- 120V Direct Wire - No Driver Needed

	Power	Comparable	Max Delivered Lumens	Color Temp	Finish
<p>WP-LED514 <i>Single</i></p>	15W	150W PAR 38	1140	30 3000K 40 4000K	ABZ Architectural Bronze ABK Architectural Black AGH Architectural Graphite AWT Architectural White
<p>WP-LED529 <i>Double</i></p>	30W	150W x 2 PAR38	1140 x 2	30 3000K 40 4000K	ABZ Architectural Bronze ABK Architectural Black AGH Architectural Graphite AWT Architectural White

Example: WP-LED514-30-ABZ



FIN



Tempered Prismatic Glass
Reduces glare while optimizing light distribution

Input: 120V-277V
CRI: 85
Dimming: 100% - 10% ELV or 0-10V
Rated Life: 100,000 hours

- Factory-Sealed LED Light Engine
- Die-cast Aluminum Construction
- 20° Forward Throw Illumination
- Built-in Level For Easy Adjustment
- Photo/Motion Sensor Sold Separately

	Power	Comparable	Max Delivered Lumens	Color Temp	Finish	
	WP-LED119	19W	39W HID	1460	30 3000K 50 5000K	ABZ Architectural Bronze
	WP-LED127	27W	70W HID	2135		AGH Architectural Graphite
	WP-LED135	35W	100W HID	2825		AWT Architectural White

Example: WP-LED127-30-AGH

MOTION SENSOR (120V) available in 3 complementary colors

MS-120-BZ Bronze

MS-120-GY Gray

MS-120-WT White

PHOTOSENSOR (120V) available in 3 complementary colors

PC-120-BZ Bronze

PC-120-GY Gray

PC-120-WT White

HAWK



Mounts in any orientation
For direct and indirect illumination



Includes box sleeve
For use with surface
mount junction boxes

Input: 120V-277V

CRI: 85

Dimming: 100% - 10% ELV or 0-10V

Rated Life: 100,000 hours

- Factory-Sealed LED Light Engine
- Die-cast Aluminum Construction
- 20° Forward Throw Illumination

- Built-in Level For Easy Adjustment
- Photo/Motion Sensor Sold Separately

	Power	Comparable	Max Delivered Lumens	Color Temp	Finish
	WP-LED219 19W	39W HID	1435	30 3000K	ABZ Architectural Bronze
	WP-LED227 27W	70W HID	2095	50 5000K	AGH Architectural Graphite
					AWT Architectural White


Example: WP-LED219-30-ABZ

MOTION SENSOR (120V) available in 3 complementary colors



MS-120-BZ	Bronze	
MS-120-GY	Gray	
MS-120-WT	White	

PHOTOSENSOR (120V) available in 3 complementary colors



PC-120-BZ	Bronze	
PC-120-GY	Gray	
PC-120-WT	White	

RUBIX & SCOOP LED DECORATIVE WALL MOUNTS

Color Temp: 3000K
CRI: 90

Dimming: 100% - 10% ELV or 0-10V
Rated Life: 70,000 hours

- Mounts up or down
- Die-cast aluminum construction

WALL MOUNT



Single light
WS-W2504

Beam: 86°
Wattage: 16W
Lumens: 750
Input: 120-277V

Up & Down light
WS-W2505

Beam: 86°
Wattage: 30W
Lumens: 1400
Input: 120-277V

Model	Finish
	AL Brushed Aluminum
	BK Black
	BZ Bronze
	GH Graphite
	WT White

Example: WS-W2504-BZ

SCOOP WALL MOUNT



Beam: 70°
Wattage: 16W
Lumens: 805
Input: 120-277V

Model	Finish
	AL Brushed Aluminum
	BK Black
	BZ Bronze
	GH Graphite
	WT White

Example: WS-W20506-BK

WALL MOUNT

- Mounts up or down
- Die-cast aluminum construction



Single light
WS-W2509

Beam: 75°
Wattage: 16W
Lumens: 805
Input: 120-277V

Model	Finish
	AL Brushed Aluminum
	BK Black
	BZ Bronze
	GH Graphite
	WT White

Example: WS-W2509-WT



Up & Down light
WS-W2510

Beam: 75°
Wattage: 30W
Lumens: 1385
Input: 120-277V

Model	Finish
	AL Brushed Aluminum
	BK Black
	BZ Bronze
	GH Graphite
	WT White

Example: WS-W2510-WT

TUBE LED DECORATIVE WALL MOUNTS



TITLE 24
CALIFORNIA

Color Temp: 3000K
CRI: 90

Dimming: 100% - 10% ELV or 0-10V
Rated Life: 70,000 hours

4" SINGLE LIGHT WALL MOUNT



Beam: 33°
Wattage: 16W
Lumens: 800
Input: 120-277V

- Mounts up or down
- Die-cast aluminum construction

	Model	Finish
	WS-W2605	AL Brushed Aluminum
		BK Black
		BZ Bronze
		GH Graphite
		WT White

Example: WS-W2605-AL

4" DOUBLE LIGHT WALL MOUNT



Beam: 33°
Wattage: 30W
Lumens: 1750
Input: 120-277V

- Die-cast aluminum construction

	Model	Finish
	WS-W2604	AL Brushed Aluminum
		BK Black
		BZ Bronze
		GH Graphite
		WT White

Example: WS-W2604-BZ

SINGLE LIGHT WALL MOUNT



Beam: 70°
Wattage: 16W
Lumens: 825
Input: 120-277V

- Mounts up or down
- Die-cast aluminum construction

	Model	Finish
	WS-W2609	AL Brushed Aluminum
		BK Black
		BZ Bronze
		GH Graphite
		WT White

Example: WS-W2609-BK

DOUBLE LIGHT WALL MOUNT



Beam: 70°
Wattage: 30W
Lumens: 1525
Input: 120-277V

- Die-cast aluminum construction

	Model	Finish
	WS-W2610	AL Brushed Aluminum
		BK Black
		BZ Bronze
		GH Graphite
		WT White

Example: WS-W2610-WT

RUBIX LED DECORATIVE CEILING MOUNTS

Color Temp: 3000K Dimming: 100% - 10% ELV or 0-10V
 CRI: 90 Rated Life: 70,000 hours



Beam: 86° • Ceiling mount
 Wattage: 16W • Die-cast aluminum construction
 Lumens: 750
 Input: 120-277V

Beam: 95° • Ceiling mount
 Wattage: 30W • Die-cast aluminum construction
 Lumens: 1875
 Input: 120-277V

	Model	Finish
	FM-W2505	AL Brushed Aluminum
		BK Black
		BZ Bronze
		GH Graphite
		WT White

	Model	Finish
	FM-W2510	AL Brushed Aluminum
		BK Black
		BZ Bronze
		GH Graphite
		WT White

Example: FM-W2505-WT

Example: FM-W2510-BZ

TUBE LED DECORATIVE CEILING MOUNT



Beam: 35° • Ceiling mount
 Wattage: 16W • Die-cast aluminum construction
 Lumens: 800 • Dark Sky Friendly
 Input: 120-277V

Beam: 91° • Ceiling mount
 Wattage: 30W • Die-cast aluminum construction
 Lumens: 1740
 Input: 120-277V

	Model	Finish
	FM-W2605	AL Brushed Aluminum
		BK Black
		BZ Bronze
		GH Graphite
		WT White

	Model	Finish
	FM-W2612	AL Brushed Aluminum
		BK Black
		BZ Bronze
		GH Graphite
		WT White

Example: FM-W2605-WT

Example: FM-W2612-GH

TUBE LED DECORATIVE CEILING MOUNT

PENDANT



Beam: 33°
 Wattage: 16W
 Lumens: 800
 Input: 120-277V

- Die-cast aluminum construction
- Hang straight swivel
- Three 12" and one 6" down rods included
- Dark Sky Friendly

		<i>Finish</i>
	PD-W2605	AL <i>Brushed Aluminum</i> BK <i>Black</i> BZ <i>Bronze</i> GH <i>Graphite</i> WT <i>White</i>

Example: PD-W2605-BK



Numerical index

SYMBOLS

1000-CON-PVC26
 101126
 102126
 105126
 2000-CON-PVC26
 201126
 201226
 202126
 202226
 203124
 204132
 205126
 205226
 206132
 207128
 208128
 301130
 302130
 303130
 401132
 402132
 5000-LCO 8, 10, 12
 5000-SCP 8, 10, 12, 34, 36, 38, 40, 42, 44, 54
 5000-TCP 8, 10, 12
 5000-X 8, 10, 12
 5010-LSHR 8, 66
 5011-CC 17
 5012 69
 5021-CC 17
 5022 69
 5030-GRD 16
 5030-PIP-PVC 16
 5031-CC 17
 5032 69
 5111-LSHR 10, 54, 66
 6011 48
 6021 38
 6031 46
 6041 50
 6051 52
 6061 40
 6071 42
 6081 34
 6091 44
 6111 54
 6211 54
 6311 36
 6321 36
 6611 58
 6612 58
 6613 58
 6621 62
 6622 62
 6623 62
 6631 60

6632 60
 6633 60
 6641 64
 6642 64
 6643 64
 6651 56
 7031 20
 7061 20
 7121 20
 7181 20
 8000 22
 8001 22
 8002 22
 8003 22
 8011 22
 8051 22
 8101 22
 9000-MTI-WT 66
 9000-PCH-GY 66
 9000-PCR-GY 6..... 6
 9000-RPT 8, 12
 9000-SP9 8, 10, 12, 34, 36, 38, 40, 42, 44, 48, 50, 52, 54
 9000-ST98, 10, 12, 34, 36, 38, 40, 42, 44, 48, 50, 52
 9020-WNT 66
 9075-TRN-SS 66
 9100 66
 9150-TRN-SS 66
 9250 66
 9300-TRN-SS 66
 9500 66
 9600-TRN-SS 66

E

EN-2460-RB2-T 72, 73
 EN-O24100-RB2-T 72, 73
 EN-OD24100-RB2-T 72

F

FM-W2505 87
 FM-W2510 87
 FM-W2605 87
 FM-W2612 87

Numerical index

L

LED-TCO	73
LED-TO24	72
LED-TO24-C1	22, 72, 74
LED-TO24-C2	22, 72, 74
LED-TO24-C3	22, 72, 74
LED-TO24-CH5	22, 72, 74
LED-TO24-CM	73
LED-TO24-CS	73
LED-TO24-EC	22, 72, 74
LED-TO24-IC	72
LED-TO24-IC	73
LED-TO24-IC6	72
LED-TO24-IC6-RGB	73
LED-TO24-IC12	72
LED-TO24-IC12-RGB	73
LED-TO24-IC72	72
LED-TO24-IC72-RGB	73
LED-TO24-IC120	72
LED-TO24-IC120-RGB	73
LED-TO24-MW	73
LED-TO24-MW60	73
LED-TO24-MW120	73
LED-TO24-SW	73
LED-TO24-SW60	73
LED-TO24-SW120	73
LED-TO24-WS	73
LED-TO24-X	72
LED-TO24-X-RGB	73
LED-TO24-Y	72
LED-TO24-Y-RGB	72, 73
LENS-2X4	12
LENS-16	10
LENS-25	16

M

M6000-STAKE	56
MS-120	78, 79, 80, 83, 84

P

PC-120	78, 79, 80, 83, 84
PD-W2605	88

W

WL-5105	76
WL-5205	76
WL-LED100	32
WL-LED200	32
WP-LED119	83
WP-LED127	83
WP-LED135	83
WP-LED219	84
WP-LED227	84
WP-LED335	78
WP-LED415	79
WP-LED430	80
WP-LED514	82
WP-LED529	82
WS-W2504	85
WS-W2505	85
WS-W2509	85
WS-W2510	85
WS-W2604	86
WS-W2605	86
WS-W2609	86
WS-W2610	86
WS-W20506	85



WAC

LANDSCAPE LIGHTING

Many LED luminaire designs within contain patent pending features.

WAC Lighting will not hesitate to enforce its intellectual property rights through injunctive relief and seek further relief through damages if it has reason to believe the patents are being infringed upon.

WAC Lighting retains the right to modify the design of our products at any time as part of the company's continuous improvement program.

Please refer to our website for the latest product specifications. Copyright 2017
waclandscapelighting.com