



AF><



An industry leader in LED, fluorescent and other light sources, we have maintained our respected position in the lighting industry. Our growth has paralleled the development and advancement of energy-efficient fluorescent and LED lighting.

By fully understanding the needs and expectations of our customers, we will continue advancing the use of sustainable LED lighting solutions with the focus of reducing energy consumption, operating and maintenance costs.

With versatile, energy-efficient lighting solutions for a wide-range of commercial and residential applications, AFX products provide the performance you need in decorative designs that blend with any architectural style.

lighting your vision.

KEY

LED



Dimmable Option



American Disability Act



Fluorescent



Wet Location



Title 24



Design Lights Consortium™



Emergency Battery Backup



ENERGY STAR® Qualified



Lighting For Tomorrow



Pendant

p.11

Sconce

p.59

Ceiling

p.119

Vanity

p.167

Fixed Rail

p.195

Outdoor

p.209

Overbed

p.247

Linear

p.265

Undercabinet

p.281

Hera

p.293

Reference/Index

p.300

Pendant



Echo p.12



Boon Drum p.15



Boon p.17



Ash Drum p.18



Elise p.20



Ash p.21



Evanston p.22



Point p.25



Manhattan p.27



Brooklyn p. 28



Roxy p.31



Oketo p.32



Mila p.33



Isla p.34



Cleo p.35



Lola p.36



Callie p.37



London p.39



Spun p.41



Hermosa p.43



Armitage p.45



View p.47



Soho p.47



Essex p.49



Geo p.50



Bella p.51



Dayton p.52



Apex p.54



Montclair p.55



Anton p.56



Sanibel p.57



Cortez p.58

Sconce



Commons p.60



Bowen p.63



Ion p.64



Rowan p.67



Summit p.68



Paulina p.70



Sorrento p.71



Storm p.72



Charlotte p.75



Arden p.77



Sinclair p.78



Fulton p.81



Post p.83



Gallery p.84



Novara p.85



Apex p.87



Aberdeen p.89



Eden p.90



Wells p.91



Cortez p.92



Casino p.94



Zoe p.95



Delany p.96



Naples p.97



Tory p.98



Sheridan p.101



Nolan p.103



Montrose p.104



Taylor p.105



Lancet p.107



Algiers p.108



Arlo p.109



Fusion p.110



Brio p.111



Century p.112



Ideal p.113

Sconce Continued



Plane p.114



Eclipse p.114



Ventura p.116



Dorset p.117



Opus p.117



Unity p.117



Radio City p.118

Ceiling



Clara p.120



Lambert p.123



Reeves p.124



Ash p.126



Boon p.127



Tatum p.129



Alta p.130



Revel p.132



Lenox p.133



Pearson p.134



Octavia p.136



Ashland p.137



Sinclair p.138



Sloane p.139



Zurich p.140



Atlas p.141



Montclair p.142



Acadia p.143



Apex p.144



Cortez p.145



Sanibel p.146



Anton p.147



Sutton p.148



Lima p.149



Delany p.150

Ceiling Continued



Monroe p.151



Sheridan p.152



Hudson p.153



Bilbao p.154



Fusion p.155



Carlisle p.165



Ideal p.158



Covina p.159



Capri p.160



Camden p.161



Cirrus p.162



Carter p.163



Edge Round p.164



Edge Square p.165

Vanity



Ryland p.169



Boon p.170



Avanti p.171



Apex p.172



Allen p.173



Rowan p.175



Arlo p.176



Arden p.177



Novara p.178



Fulton p.180



Aria p.182



Charlotte p.183



Algiers p.184



Fusion p.186



Century p.187



Rio p.188

Vanity Continued



Sinclair p.189



Bilbao p.190



Vernon p.191



Hollywood p.192



Pacific p.193




Stratus p.194


Fixed Rail




District p.197



Chappelle p.134




Metro p.200




Core p.201



Gramercy p.203




Cantrell p.204



Acadia p.205



Satellite p.206



Berlin p.207



Madrid p.208

Outdoor



Rowan p.211



Avenue p.212



Beaumont p.213



Boon p.215



Concord p.216



Lasalle p.218



Knox p.219



Colton p.220



Dakota p.221



Pasadena p.223



Broadway p.224



Paxon p.225

Outdoor Continued



Stack p.226



Beaumont p.228



Blaine p.229



Logan p.231



Avenue p.232



Max p.234



State p.235



Brio p.237



Everly p.238



Cape p.239



Olden p.240



Dawson p.240



Bristol p.240



Butler p.241



Patriot p.241



Clark p.241



Stratford p.242



Newport p.242



Ventura p.242



LED Wall Packs
p.243-244



LED Flood/Utility
p.244-245



LED Security
p.245

Overbed



Hayes p.248



Allen p.249



Apex p.250



Scott p.252



Marquette p.253



Harvard p.254



Randolph p.255



Clayton p.256



Sheffield p.257



Algiers p.258



Sheridan p.259



Ideal p.261



Hinsdale p.262



Cameron p.263



Palmetto p.264

Linear




Zurich p.266



Sloane p.267



Atlas p.268



Aeon p.269



Winchester p.270



Nimbus p.270



LED Cloud p.271



Rigby p.271



Shaw p.272



Spring p.272



Pierce p.273



Warsaw p.273



Lotus p.274



Fluorescent Wrap p.274



LED Wrap p.276



Coronado p.277



Lisle p.277



Standard Striplight p.278



Commercial Striplight p.279



Low-Profile Striplight p.279



LED Vaportite p.280



Vaportite p.280


Undercabinet



Slate Pro 2.0 p.285




Koren p.286



LED Noble Pro p.288



LED T5L p.290



T5L Closet P.291

PENDANT



Black/Gold

ECHO

- Metal housing
- Powder coat finish
- Up/down light
- 9 ft. adjustable cable

LED

- 120-277V universal-voltage driver
- User selectable CCT adjustment
- Touch sensor for dimming
- 50,000 hr. LED life, 90 CRI



Touch Sensor Features:

- Hold for full range dimming
- One touch color temperature change

Black/Gold	White	LED	Source Lumens	Adjustable CCT	L	W	D
ECHP4830LAJMV BK	ECHP4830LAJMV WH	37W	3000	3000K/3500K/4000K	44-3/4"	2"	8"





PENDANT





White

BOON DRUM

- Metal housing
- Edge-lit light panel
- Low-profile design
- 9 ft. adjustable cable


LED

- 120V TRIAC dimmable
- 50,000 hr. LED life, 90 CRI

Black	White	LED	Source Lumens	CCT	DIA.	H
BONP2032L30D1BK	BONP2032L30D1WH	36W	3000	3000K	20"	8-1/2"

LED **DIM**

Companions







White

BOON

- Decorative cut metal cylinder
- Powder coat finish
- 9 ft. adjustable cord

LED

- 120-277V universal-voltage driver, 0-10V dimming
- 50,000 hr. LED life, 90 CRI

Black	White	LED	Source Lumens	CCT	DIA.	H
BONP0407L30D2BK	BONP0407L30D2WH	12W	780	3000K	3-1/2"	12"



Companions



PENDANT



Black/Gold

ASH DRUM

- Metal perforated ring
- Powder coated finish
- White acrylic diffuser
- 9 ft. adjustable cable


LED

- 120V TRIAC dimmable
- 50,000 hr. LED life, 90 CRI

Black/Gold	White	LED	Source Lumens	CCT	DIA.	H
ASHP2032L30D1BK	ASHP2032L30D1WH	36W	3000	3000K	20"	8-1/2"

LED **DIM**

Companions





PENDANT

White Ash Drum Shown



ELISE

- Metal band accent
- Faceted glass diffuser
- 9 ft. adjustable cord

LED

- 120-277V universal-voltage driver, 0-10V dimming
- 50,000 hr. LED life, 90 CRI

	Source			
Satin Nickel	LED	Lumens	CCT	DIA. H
ELEP0407L30D2SN	12W	780	3000K	3-3/4" 12"

LED **DIM**





White



Black/Gold

ASH

- Metal perforated cylinder
- Powder coat finish
- 9 ft. adjustable cord

LED

- 120-277V universal-voltage driver, 0-10V dimming
- 50,000 hr. LED life, 90 CRI

Black/Gold	White	LED	Source Lumens	CCT	DIA.	H
ASHP0407L30D2BK	ASHP0407L30D2WH	12W	780	3000K	3-1/2"	12"

LED **DIM**

Companions





EVANSTON

- Cream linen shade
- Satin nickel accent detail
- White bottom acrylic diffuser
- 3 ft. adjustable rigid stem expandable up to 9 ft.
- Additional stems sold separately

LED

- 120-277V universal-voltage driver
- Compatible with residential (TRIAC/ELV) and commercial (0-10V) dimmers
- TRIAC and ELV dimming only at 120V
- 50,000 hr. LED life, 90 CRI
- Adjustable CCT

Satin Nickel	LED	Source Lumens	Adjustable CCT	DIA.	H
EVNP2532LAJUDSN	35W	3200	3000K/3500K/4000K	25"	12"

LED
DIM
3in1 color temperature
 3000K/3500K/4000K





PENDANT





POINT

- Thin cylinder with powder coat finish
- 9 ft. adjustable cable

LED

- 120V operation non-dimmable (1-Point)
- 120V TRIAC dimmable (3-Point)
- 50,000 hr. LED life, 90 CRI

1-Point


Satin Nickel	Polished Chrome	Black	White	LED	Source Lumens	CCT	DIA.	H
PNTP0102L30ENSN	PNTP0102L30ENPC	PNTP0102L30ENBK	PNTP0102L30ENWH	3W	240	3000K	4-1/4"	14"


LED

3-Point

Satin Nickel	Polished Chrome	Black	White	LED	Source Lumens	CCT	DIA.	H
PNTP0107L30ENSN	PNTP0107L30ENPC	PNTP0107L30ENBK	PNTP0107L30ENWH	9W	720	3000K	4-1/4"	18"

LED DIM





MANHATTAN

- Decorative cut metal cylinder
- 9 ft. adjustable cord

LED

- 120-277V universal-voltage driver, 0-10V dimming
- 50,000 hr. LED life, 90 CRI

Brushed Chrome	LED	Source Lumens	CCT	DIA.	H
MHNP0407L30D2BC	12W	780	3000K	4"	12-3/4"



Lit



Unlit

PENDANT




Silver

BROOKLYN

- Solid metal diffuser
- 9 ft. adjustable cord
- Medium base socket, 60W MAX*

Antique Brass	Silver	Qty.	Lamp	DIA.	H
BKNP10QB	BKNP10SL	1	60W (MAX)*	9-1/2"	10"
BKNP16QB	BKNP16SL	1	60W (MAX)*	15-3/4"	14-1/2"

*Sockets can be labeled for reduced wattage upon request





Antique
Brass

PENDANT



Black




ROXY

- Solid metal diffuser
- 9 ft. adjustable cord
- Medium base socket, 60W MAX*

White	Black	Qty.	Lamp	DIA.	H
RXYP08WH	RXYP08BK	1	60W (MAX)*	7-7/8"	6-1/4"
RXYP12WH	RXYP12BK	1	60W (MAX)*	11-7/8"	10"


*Sockets can be labeled for reduced wattage upon request



PENDANT

White Roxy Shown





OKETO

- Metal cylinder with powder coat finish
- 9 ft. adjustable cable

LED

- 120-277V universal-voltage driver
- Compatible with residential (TRIAC/ELV) and commercial (0-10V) dimmers
- TRIAC and ELV dimming only at 120V
- 50,000 hr. LED life, 90 CRI

Black	Silver	White	LED	Source Lumens	CCT	DIA.	H
OTPO21207L30UDBK	OTPO21207L30UDSL	OTPO21207L30UDWH	12W	780	3000K	2"	12"



Copper

Smoke




MILA

- Hand-blown colored ribbed glass with metallic coating
- 9 ft. adjustable cord
- Medium base socket, 60W MAX*

Copper	Smoke	Qty.	Lamp	DIA.	H
MLAP13CP	MLAP13SM	1	60W (MAX)*	6"	13"

*Sockets can be labeled for reduced wattage upon request



PENDANT



ISLA

- Hand-blown frosted ribbed white glass
- 9 ft. adjustable cord
- Medium base socket, 60W MAX*

White	Qty.	Lamp	DIA.	H
ISLP11WH	1	60W (MAX)*	11"	16"

*Sockets can be labeled for reduced wattage upon request



H-Ø DIA.-H



CLEO

- Hand-blown frosted ribbed white glass
- 9 ft. adjustable cord
- Medium base socket, 60W MAX*

White	Qty.	Lamp	DIA.	H
CLEP13WH	1	60W (MAX)*	12-1/2"	13-3/4"

*Sockets can be labeled for reduced wattage upon request





LOLA

- Hand-blown frosted ribbed white glass
- 9 ft. adjustable cord
- Medium base socket, 60W MAX*

White	Qty.	Lamp	DIA.	H
LOLP11WH	1	60W (MAX)*	11"	18-1/4"

*Sockets can be labeled for reduced wattage upon request





CALLIE

- Hand-blown frosted ribbed white glass
- 9 ft. adjustable cord
- Medium base socket, 60W MAX*

White	Qty.	Lamp	DIA.	H
CALP05WH	1	60W (MAX)*	5-1/2"	8"
CALP09WH	1	60W (MAX)*	9"	15-1/4"

*Sockets can be labeled for reduced wattage upon request







PENDANT

LONDON


- Metal cap
- Hand-blown glass diffuser
- 9 ft. adjustable cable

LED

- 120-277V universal-voltage driver
- 0-10V dimming
- 50,000 hr. LED life, 90 CRI

Polished Nickel	LED	Source Lumens	CCT	DIA.	H
SLDNP02L1-PN	7W	550	3000K	3"	6"

LED DIM





Clear



Smoke



Steel Blue



SPUN

- Hand-blown glass with white pattern molten glass cane
- White inner glass
- 9 ft. adjustable cord with twist lock strain relief

LED

- 50,000 hr. LED life, available in 1000 lumens (10W), 90 CRI

5" DIA. x 16-3/4" H

Series	Source Lumens	LED L	CCT	Driver	Finish	Glass	Canopy Options
SPP	1000	L	30 3000K 40 4000K	D1 Voltage (120V TRIAC Dimming) D2 Voltage (120-277V 0-10V Dimming)	SN Satin Nickel	CL Clear SM Smoke SB Steel Blue	Blank Monopoint LNR3 (3) Light Linear RND3 (3) Light Round RND6 (6) Light Round

Example: SPP1000L30D2SNSMLNR3



PENDANT



Clear Swirl



Brown



Aqua



Clear

HERMOSA

- Clear or tinted outer glass
- White inner glass
- 9 ft. adjustable cord with twist lock strain relief

LED

- 50,000 hr. LED life, available in 1000 lumens (10W), 90 CRI

6" DIA. x 16" H

Series HRP	Source Lumens 1000	LED L	CCT 30 3000K 40 4000K	Driver D1 Voltage (120V TRIAC Dimming) D2 Voltage (120-277V 0-10V Dimming)	Finish SN Satin Nickel	Glass AQ Aqua CL Clear CS Clear Swirl BR Brown	Canopy Options Blank Monopoint LNR3 (3) Light Linear RND3 (3) Light Round RND6 (6) Light Round
----------------------	------------------------------	-----------------	------------------------------------	---	----------------------------------	---	---

Example: HRP1000L40D1SNAQ



The image displays three conical pendant lights against a light gray background. The top light is a dark brown color with a smooth, reflective surface. The middle light is clear glass with a crackle or textured finish. The bottom light is clear glass with a smooth, polished surface. Each light is illuminated from within, casting a warm glow. The lights are suspended by thin black cords.

Brown

Clear Crackle

Clear



ARMITAGE

- Clear or tinted outer glass
- White inner glass
- 9 ft. adjustable cable with twist lock strain relief

LED

- 50,000 hr. LED life, available in 500 lumens (6W), 90 CRI

10" DIA. x 8" H

Series	Source Lumens	LED L	CCT	Driver	Finish	Glass
AGP	500	L	30 3000K 40 4000K	D1 Voltage (120V TRIAC Dimming) D2 Voltage (120-277V 0-10V Dimming)	SN Satin Nickel	AQ Aqua CC Clear Crackle CL Clear BR Brown

Example: AGP500L30DISNCL



PENDANT



White

VIEW

- Frosted inner glass
- Clear outer glass
- 9 ft. adjustable cord with twist lock strain relief

LED

- 50,000 hr. LED life, available in 1000 lumens (10W), 90 CRI



Amber


Cream

White

4-5/8" DIA. x 16" H

Series VIP	Source Lumens 1000	LED L	CCT 30 3000K 40 4000K	Driver D1 Voltage (120V TRIAC Dimming) D2 Voltage (120-277V 0-10V Dimming)	Finish SN Satin Nickel	Glass AM Amber CR Cream WH White	Canopy Options Blank Monopoint LNR3 (3) Light Linear RND3 (3) Light Round RND6 (6) Light Round
----------------------	------------------------------	-----------------	------------------------------------	---	----------------------------------	--	---

Example: VIP1000L40D1SNCRNRND6



SOHO

- Frosted glass
- 9 ft. adjustable cord with twist lock strain relief

LED

- 50,000 hr. LED life, available in 1000 lumens (10W), 90 CRI



Amber


Cream

White

3-7/8" DIA. x 14" H

Series SSP	Source Lumens 1000	LED L	CCT 30 3000K 40 4000K	Driver D1 Voltage (120V TRIAC Dimming) D2 Voltage (120-277V 0-10V Dimming)	Finish SN Satin Nickel	Glass AM Amber CR Cream WH White	Canopy Options Blank Monopoint LNR3 (3) Light Linear RND3 (3) Light Round RND6 (6) Light Round
----------------------	------------------------------	-----------------	------------------------------------	---	----------------------------------	--	---

Example: SSP1000L40D2SNWH





Red

White

Blue



Amber

ESSEX

- Mini glass pendant
- 9 ft. adjustable cable

LED

- 50,000 hr. LED life, available in 500 lumens (6W), 90 CRI

4-1/4" DIA. x 5" H

Series	Source Lumens	LED	CCT	Driver	Finish	Glass	Canopy Options
SXPL	500	L	30 3000K 40 4000K	D1 Voltage (120V TRIAC Dimming) D2 Voltage (120-277V 0-10V Dimming)	SN Satin Nickel	AM Amber BU Blue RD Red WH White	Blank Monopoint LNR3 (3) Light Linear RND3 (3) Light Round RND6 (6) Light Round

Example: SXPL500L40D2SNWH





GEO

- Mini glass pendant
- 9 ft. adjustable cable


LED

- 50,000 hr. LED life, available in 500 lumens (6W), 90 CRI

3-1/8" DIA. x 3-7/8" H

Series	Source Lumens	LED	CCT	Driver	Finish	Glass	Canopy Options
GEPL	500	L	30 3000K 40 4000K	D1 Voltage (120V TRIAC Dimming) D2 Voltage (120-277V 0-10V Dimming)	SN Satin Nickel	WH White	Blank Monopoint LNR3 (3) Light Linear RND3 (3) Light Round RND6 (6) Light Round

Example: GEPL500L30D2SNWH





Red

BELLA

- Mini glass pendant
- 9 ft. adjustable cable

LED

- 50,000 hr. LED life, available in 500 lumens (6W), 90 CRI

3-3/8" DIA. x 6-1/2" H




Amber

Blue

White

Series	Source Lumens	LED	CCT	Driver	Finish	Glass	Canopy Options
BEPL	500	L	30 3000K 40 4000K	D1 Voltage (120V TRIAC Dimming) D2 Voltage (120-277V 0-10V Dimming)	SN Satin Nickel	AM Amber BU Blue RD Red WH White	Blank Monopoint LNR3 (3) Light Linear RND3 (3) Light Round RND6 (6) Light Round

Example: BEPL500L30D1SNRD






DAYTON

- Two-tier white linen fabric shade
- White bottom acrylic diffuser
- Adjustable aircraft cable provided
- 3 ft. adjustable rigid stem expandable up to 9 ft.
- Additional stems sold separately

LED

- 120-277V universal-voltage driver
- Compatible with residential (TRIAC/ELV) and commercial (0-10V) dimmers
- TRIAC and ELV dimming only at 120V
- 50,000 hr. LED life, 90 CRI
- Adjustable CCT

Satin Nickel	LED	Source Lumens	Adjustable CCT	DIA.	H
DYP2432LAJUDSN	35W	3200	3000K/3500K/4000K	24"	9"
DYP3044LAJUDSN	46W	4400	3000K/3500K/4000K	30"	12"





PENDANT



Espresso/Jute

APEX

- Solid wood accent detail
- LumaFuse™ laminated fabric/acrylic shade
- White bottom acrylic diffuser
- Adjustable aircraft cable provided
- 3 ft. adjustable rigid stem expandable up to 9 ft.
- Additional stems sold separately

LED


- 120-277V universal-voltage driver
- Compatible with residential (TRIAC/ELV) and commercial (0-10V) dimmers
- TRIAC and ELV dimming only at 120V
- 50,000 hr. LED life, 90 CRI
- Adjustable CCT



Weathered Grey/
Linen White

Espresso/Jute		Weathered Grey/Jute		LED	Source Lumens	Adjustable CCT	DIA.	H
APP1214LAJUDSNES-JT	APP1214LAJUDSNWG-JT	18W	1400	3000K/3500K/4000K	14-1/4"	4-1/4"		
APP1524LAJUDSNES-JT	APP1524LAJUDSNWG-JT	30W	2400	3000K/3500K/4000K	17"	4-1/4"		
APP1932LAJUDSNES-JT	APP1932LAJUDSNWG-JT	42W	3200	3000K/3500K/4000K	21-1/4"	4-1/4"		

Espresso/Linen White		Weathered Grey/Linen White		LED	Source Lumens	Adjustable CCT	DIA.	H
APP1214LAJUDSNES-LW	APP1214LAJUDSNWG-LW	18W	1400	3000K/3500K/4000K	14-1/4"	4-1/4"		
APP1524LAJUDSNES-LW	APP1524LAJUDSNWG-LW	30W	2400	3000K/3500K/4000K	17"	4-1/4"		
APP1932LAJUDSNES-LW	APP1932LAJUDSNWG-LW	42W	3200	3000K/3500K/4000K	21-1/4"	4-1/4"		



Companions





MONTCLAIR

- LumaFuse™ laminated fabric/acrylic shade
- Stepped white acrylic bottom diffuser
- Adjustable aircraft cable provided
- 3 ft. adjustable rigid stem expandable up to 9 ft.
- Additional stems sold separately

LED

- 120-277V universal-voltage driver
- Compatible with residential (TRIAC/ELV) and commercial (0-10V) dimmers
- TRIAC and ELV dimming only at 120V
- 50,000 hr. LED life, 90 CRI
- Adjustable CCT

Satin Nickel/Black	LED	Source Lumens	Adjustable CCT	DIA.	H
MCP1214LAJUDSN-BK	18W	1400	3000K/3500K/4000K	12-1/4"	3-3/4"
MCP1524LAJUDSN-BK	30W	2400	3000K/3500K/4000K	15"	4-3/4"
MCP1932LAJUDSN-BK	42W	3200	3000K/3500K/4000K	19-1/4"	5-1/2"



Companion





Jute

ANTON

- LumaFuse™ laminated fabric/acrylic shade
- White bottom acrylic diffuser
- Adjustable aircraft cable provided
- 3 ft. adjustable rigid stem expandable up to 9 ft.
- Additional stems sold separately

LED

- 120-277V universal-voltage driver
- Compatible with residential (TRIAC/ELV) and commercial (0-10V) dimmers
- TRIAC and ELV dimming only at 120V
- 50,000 hr. LED life, 90 CRI
- Adjustable CCT



Linen White

Satin Nickel/Jute	Satin Nickel/Linen White	LED	Source Lumens	Adjustable CCT	DIA.	H
ANP1214LAJUDSN-JT	ANP1214LAJUDSN-LW	18W	1400	3000K/3500K/4000K	12-1/4"	4-3/4"
ANP1524LAJUDSN-JT	ANP1524LAJUDSN-LW	30W	2400	3000K/3500K/4000K	15"	5-1/2"
ANP1932LAJUDSN-JT	ANP1932LAJUDSN-LW	42W	3200	3000K/3500K/4000K	19-1/4"	5-1/2"



Jute



Linen White

Companion





Linen White

SANIBEL

- LumaFuse™ laminated fabric/acrylic shade
- White bottom acrylic diffuser
- Adjustable aircraft cable provided
- 3 ft. adjustable rigid stem expandable up to 9 ft.
- Additional stems sold separately

LED

- 120-277V universal-voltage driver
- Compatible with residential (TRIAC/ELV) and commercial (0-10V) dimmers
- TRIAC and ELV dimming only at 120V
- 50,000 hr. LED life, 90 CRI
- Adjustable CCT



Jute

		LED	Source Lumens	Adjustable CCT	DIA.	H
Satin Nickel/Jute	Satin Nickel/Linen White	18W	1400	3000K/3500K/4000K	16"	5-5/8"
SAP1614LAJUDSN-JT	SAP1614LAJUDSN-LW	30W	2400	3000K/3500K/4000K	18"	5-5/8"
SAP1824LAJUDSN-JT	SAP1824LAJUDSN-LW	42W	3200	3000K/3500K/4000K	23-1/4"	5-5/8"



Companion





White/White

CORTEZ

- Sheer organza fabric outer shade
- White linen inner shade
- White acrylic bottom diffuser
- Adjustable aircraft cable provided
- 3 ft. adjustable rigid stem expandable up to 9 ft.
- Additional stems sold separately

LED

- 120-277V universal-voltage driver
- Compatible with residential (TRIAC/ELV) and commercial (0-10V) dimmers
- TRIAC and ELV dimming only at 120V
- 50,000 hr. LED life, 90 CRI
- Adjustable CCT



Bronze/White

Satin Nickel/White

CZP2432LAJUDSN-WHWH
CZP3044LAJUDSN-WHWH

Satin Nickel/Bronze

CZP2432LAJUDSN-BZWH
CZP3044LAJUDSN-BZWH

LED
42W
60W

Source Lumens
3200
4400

Adjustable CCT
3000K/3500K/4000K
3000K/3500K/4000K

DIA. H
24" 5"
30" 6"

Oakley Bronze/White

CZP2432LAJUDKB-WHWH
CZP3044LAJUDKB-WHWH

Oakley Bronze/Bronze



CZP2432LAJUDKB-BZWH
CZP3044LAJUDKB-BZWH

LED
42W
60W

Source Lumens
3200
4400

Adjustable CCT
3000K/3500K/4000K
3000K/3500K/4000K

DIA. H
24" 5"
30" 6"



Companions



SCONCE



COMMONS


- Faceted metal housing
- Metal face plate
- Durable powder coat finish
- Vertical or horizontal mounting


LED

- 120-277V universal-voltage driver, 0-10V dimming
- 50,000 hr. LED life, 90 CRI


White	LED	Source Lumens	CCT	H	W	D
CMNS070708L30D2WH	13W	800	3000K	7"	7"	2"
CMNS072716L30D2WH	24W	1600	3000K	27"	7"	2"

LED **DIM** **ADA**





SCONCE



BOWEN

- Die-cast metal backplate with accent
- White acrylic diffuser

LED

- 120V TRIAC dimmable
- 50,000 hr. LED life, 90 CRI

Satin Nickel	LED	Source Lumens	CCT	H	W	D
BWNS051412L30D1SN	15.5W	1200	3000K	14-1/4"	4-1/2"	3-3/4"

LED **DIM** **ADA**





ION

- Metal housing
- White acrylic diffuser
- Indirect light for wall wash effect
- Vertical or horizontal mounting

LED

- 120-277V universal-voltage driver, 0-10V dimming
- 50,000 hr. LED life, 90 CRI

Satin Nickel	LED	Source Lumens	CCT	H	W	D
IONS032015L30D2SN	18W	1500	3000K	20"	3-1/4"	2-1/2"





SCONCE





Satin Nickel

ROWAN

- Metal housing
- Powder coat finish
- White acrylic diffuser
- Vertical or horizontal mounting

LED


- 120-277V universal-voltage driver
- 0-10V dimming
- 50,000 hr. LED life, 90 CRI

Satin Nickel		White	LED	Source Lumens	CCT	H	W	D
RWNS180414L30D2SN	RWNS180414L30D2WH	RWNS180414L30D2WH	16W	1400	3000K	18"	4"	2-1/2"
RWNS300424L30D2SN	RWNS300424L30D2WH	RWNS300424L30D2WH	28W	2400	3000K	30"	4"	2-1/2"

LED **DIM** **ADA**



SCONCE



White/Silver

SUMMIT

- Metal housing
- Powder coat finish
- Open top and bottom
- Indirect light with wall wash effect

LED

- 120V TRIAC dimmable (D1)
- 120-277V universal non-dimmable (MV)
- 50,000 hr. LED life, 90 CRI

White/Silver		Black/Copper		LED	Source Lumens	CCT	H	W	D
SUMS051413L30D1WH		SUMS051413L30D1BK		20W	1300	3000K	14"	5"	3"
SUMS051413L30MVWH		SUMS051413L30MVBK		20W	1300	3000K	14"	5"	3"





SCONCE

Black/Copper Summit Shown





PAULINA

- Cylindrical metal base
- Cream linen shade

LED

- 120V TRIAC dimmable
- 50,000 hr. LED life, 90 CRI

Polished Chrome	LED	Source Lumens	CCT	H	W	D
PALS051412L30D1PC	15.5W	1200	3000K	13-1/2"	4-3/4"	3-1/2"

LED **DIM** **ADA**





SORRENTO


- Metal backplate and decorative band
- White acrylic diffuser

LED

- 120-277V universal-voltage driver
- Compatible with residential (TRIAC/ELV) and commercial (0-10V) dimmers
- 50,000 hr. LED life, 90 CRI
- Adjustable CCT

Satin Nickel	LED	Source Lumens	Adjustable CCT	H	W	D
SORS051914LAJUDSN	15W	1200	3000K/3500K/4000K	18-1/2"	4-3/4"	3-1/2"

LED
DIM
ADA
3in1 color temperature
 3000K/3500K/4000K





Black Chrome



Silver


STORM


- Indirect light with wall wash effect
- Edge-lit diffuser
- Vertical or horizontal mounting

LED

- 120-277V universal-voltage driver
- 0-10V dimming
- 50,000 hr. LED life, 90 CRI

Black Chrome	Silver	LED	Source Lumens	CCT	H	W	D
STMS061408L30D2BC	STMS061408L30D2SL	13W	800	3000K	14"	5-1/2"	2"









Oil-Rubbed Bronze

CHARLOTTE

- Perforated metal ends
- White linen shade


LED

- 120-277V universal-voltage driver
- Compatible with residential (TRIAC/ELV) and commercial (0-10V) dimmers
- 50,000 hr. LED life, 90 CRI
- Adjustable CCT

Satin Nickel	Oil-Rubbed Bronze	LED	Source Lumens	Adjustable CCT	H	W	D
CHS061407LAJUDSN	CHS061407LAJUDRB	9W	700	3000K/3500K/4000K	13-3/4"	5-1/2"	3-3/8"



3in1 color temperature
3000K/3500K/4000K



Companion








ARDEN

- Walnut finish
- Clear outer glass cylinder
- White inner glass cylinder

LED

- 120V TRIAC dimmable
- 50,000 hr. LED life, 90 CRI

Satin Nickel	Oil-Rubbed Bronze	LED	Source Lumens	CCT	H	W	D
RNS5161200L30D1SN	RNS5161200L30D1RB	15.5W	1200	3000K	15-3/4"	4-3/4"	4"



Companion






SINCLAIR

- Metal housing
- Frosted white acrylic diffuser
- Closed top and bottom
- Requires a rectangular 2 in. x 4 in. electrical box for installation

LED

- 120-277V universal-voltage driver
- Compatible with residential (TRIAC/ELV) and commercial (0-10V) dimmers
- 50,000 hr. LED life, 90 CRI
- Adjustable CCT

	LED	Source Lumens	Adjustable CCT	H	W	D
Satin Nickel SNS041007LAJUDSN	7W	700	3000K/3500K/4000K	10"	3-3/4"	3"
SNS041814LAJUDSN	15W	1400	3000K/3500K/4000K	18"	3-3/4"	3"



Companions





SCONCE





FULTON

- Fabricated metal housing
- White diffuser
- Powder coat finish
- Vertical or horizontal mounting

LED


- 120V TRIAC dimmable
- 50,000 hr. LED life, 90 CRI

White	Black	LED	Source Lumens	CCT	H	W	D
FTS4141200L30D1WH	FTS4141200L30D1BK	15.5W	1200	3000K	13-1/2"	4"	3-1/2"
FTS4241800L30D1WH	FTS4241800L30D1BK	23W	1800	3000K	24"	4"	3-1/2"

LED **DIM** **ADA**







Dark Grey

POST

- Combination metal and painted finish
- Indirect illumination
- Requires a rectangular 2 in. x 4 in. electrical box for installation
- Vertical or horizontal mounting

LED

- 120V TRIAC dimmable
- 50,000 hr. LED life, 90 CRI

Dark Grey	White	LED	Source Lumens	CCT	H	W	D
PTS3151200L30D1SNGY	PTS3151200L30D1SNWH	15.5W	1200	3000K	13-1/2"	3"	3-1/2"





GALLERY

- Metal backplate and decorative band
- Clear glass with printed pattern

LED

- 120V TRIAC dimmable
- 50,000 hr. LED life, 90 CRI

Satin Nickel	LED	Source Lumens	CCT	H	W	D
GLYS140512L30D1SN	15W	1200	3000K	14"	5"	2-1/2"





SCONCE

NOVARA

- Metal housing
- White acrylic diffuser
- Vertical or horizontal mounting

LED

- 120V TRIAC dimmable
- 50,000 hr. LED life, 90 CRI

Satin Nickel	Source			H	W	D
	LED	Lumens	CCT			
NVS5131200L30D1SN	15.5W	1200	3000K	13"	4-1/2"	3-5/8"
NVV5252400L30D1SN	31W	2400	3000K	25"	4-1/2"	3-5/8"

LED **DIM** **ADA**



Companion







Espresso/Jute

APEX

- Solid wood accent detail
- LumaFuse™ laminated fabric/acrylic shade
- White acrylic closed top and bottom



LED

- 120-277V universal-voltage driver
- Compatible with residential (TRIAC/ELV) and commercial (0-10V) dimmers
- TRIAC and ELV dimming only at 120V
- 50,000 hr. LED life, 90 CRI
- Adjustable CCT

Espresso/Jute	Weathered Grey/Jute	LED	Source Lumens	Adjustable CCT	H	W	D
APS051314LAJUDES-JT	APS051314LAJUDWG-JT	17W	1400	3000K/3500K/4000K	13-1/2"	5"	3"

Espresso/Linen White	Weathered Grey/Linen White	LED	Source Lumens	Adjustable CCT	H	W	D
APS051314LAJUDES-LW	APS051314LAJUDWG-LW	17W	1400	3000K/3500K/4000K	13-1/2"	5"	3"

LED
DIM
ADA
3in1^{color}
temperature
3000K/3500K/4000K



Companion





Espresso/Jute



Weathered Grey/
Linen White

ABERDEEN

- LumaFuse™ laminated fabric/acrylic shade
- Solid maple wood backplate and trim


LED

- 120-277V universal-voltage driver
- Compatible with residential (TRIAC/ELV) and commercial (0-10V) dimmers
- TRIAC and ELV dimming only at 120V
- 50,000 hr. LED life, 90 CRI
- Adjustable CCT

Espresso/ Jute	Weathered Grey/ Jute	LED	Source Lumens	Adjustable CCT	H	W	D
ADS051914LAJUDES-JT	ADS051914LAJUDWG-JT	17W	1400	3000K/3500K/4000K	19"	5-1/2"	3"

Espresso/ Linen White	Weathered Grey/ Linen White	LED	Source Lumens	Adjustable CCT	H	W	D
ADS051914LAJUDES-LW	ADS051914LAJUDES-LW	17W	1400	3000K/3500K/4000K	19"	5-1/2"	3"

LED **DIM** **ADA** **3in1** color temperature
3000K/3500K/4000K





Chocolate/
Jute


EDEN

- LumaFuse™ laminated fabric/acrylic shade
- Wood veneer trim detail
- White acrylic closed top and bottom

LED

- 120-277V universal-voltage driver
- Compatible with residential (TRIAC/ELV) and commercial (0-10V) dimmers
- 50,000 hr. LED life, 90 CRI
- Adjustable CCT

Chocolate/Jute	LED	Source Lumens	Adjustable CCT	H	W	D
EDS061114LAJUDCV-JT	17W	1400	3000K/3500K/4000K	11-1/4"	6"	3"
Chocolate/Linen White	LED	Source Lumens	Adjustable CCT	H	W	D
EDS061114LAJUDCV-LW	17W	1400	3000K/3500K/4000K	11-1/4"	6"	3"




Chocolate
Veneer



Jute



Linen
White



Espresso

WELLS

- Solid maple construction
- White acrylic diffuser

LED

- 120-277V universal-voltage driver
- Compatible with residential (TRIAC/ELV) and commercial (0-10V) dimmers
- 50,000 hr. LED life, 90 CRI
- Adjustable CCT



Weathered Grey

4-Bar Frame


Espresso	Weathered Grey	LED	Source Lumens	Adjustable CCT	H	W	D
WES071214LAJUDES4B	WES071214LAJUDWG4B	17W	1400	3000K/3500K/4000K	12"	7"	3-3/4"


6-Bar Frame

Espresso	Weathered Grey	LED	Source Lumens	Adjustable CCT	H	W	D
WES071214LAJUDES6B	WES071214LAJUDWG6B	17W	1400	3000K/3500K/4000K	12"	7"	3-3/4"



3in1 color temperature
3000K/3500K/4000K





CORTEZ

- Die-cast metal decorative accents
- Sheer organza fabric outer shade
- White linen inner shade with die-cast details

LED

- 120-277V universal-voltage driver
- Compatible with residential (TRIAC/ELV) and commercial (0-10V) dimmers
- 50,000 hr. LED life, 90 CRI
- Adjustable CCT



Satin Nickel
White/White



		LED	Source Lumens	Adjustable CCT	H	W	D
Satin Nickel/White	Satin Nickel/Bronze						
CZS062214LAJUDSN-WHWH	CZS062214LAJUDSN-BZWH	15W	1400	3000K/3500K/4000K	25"	6"	4"
CZS063121LAJUDSN-WHWH	CZS063121LAJUDSN-BZWH	23W	2100	3000K/3500K/4000K	31-1/4"	6"	4"
		LED	Source Lumens	Adjustable CCT	H	W	D
Oakley Bronze/White	Oakley Bronze/Bronze						
CZS062214LAJUDKB-WHWH	CZS062214LAJUDKB-BZWH	15W	1400	3000K/3500K/4000K	25"	6"	4"
CZS063121LAJUDKB-WHWH	CZS063121LAJUDKB-BZWH	23W	2100	3000K/3500K/4000K	31-1/4"	6"	4"




3in1 color temperature
 3000K/3500K/4000K




Companions





Oakley Bronze
Bronze/White

SCONCE



CASINO

- Modern angular design metal housing
- Painted finish

LED

- 120V TRIAC dimmable (D1)
- 120-277V universal non-dimmable (MV)
- 50,000 hr. LED life, 90 CRI



Satin Nickel

White	Satin Nickel	LED	Source Lumens	CCT	H	W	D
COS6101300L30MVWH	COS6101300L30MVSN	18W	1300	3000K	6-1/2"	10"	3-1/4"
COS6101300L30D1WH	COS6101300L30D1SN	18W	1300	3000K	6-1/2"	10"	3-1/4"





ZOE

- Cube design metal housing
- Indirect light with wall wash effect
- Painted finish

LED

- 120V TRIAC dimmable (D1)
- 120-277V universal non-dimmable (MV)
- 50,000 hr. LED life, 90 CRI

White	Black	LED	Source Lumens	CCT	H	W	D
ZOS505600L30MVWH	ZOS505600L30MVBK	9W	600	3000K	5"	5"	4"
ZOS505600L30D1WH	ZOS505600L30D1BK	9W	600	3000K	5"	5"	4"



White



DELANY


- Die-cast metal decorative accents
- Perforated top and bottom metal diffuser
- Faceted white acrylic front diffuser

LED

- 120-277V universal-voltage driver
- Compatible with residential (TRIAC/ELV) and commercial (0-10V) dimmers
- 50,000 hr. LED life, 90 CRI
- Adjustable CCT

Satin Nickel	LED	Source Lumens	Adjustable CCT	H	W	D
MIDS131514LAJUDSN	17W	1400	3000K/3500K/4000K	15"	13"	3-7/8"

LED
DIM
ADA
3in1 color temperature
3000K/3500K/4000K



Companion





NAPLES


- Metal backplate and decorative band
- White acrylic diffuser

LED

- 120V TRIAC dimmable
- 50,000 hr. LED life, 90 CRI
- Adjustable CCT

Satin Nickel | LED | Source Lumens | Adjustable CCT | H | W | D
 NPLS051610LAJD1SN | 14W | 1000 | 3000K/3500K/4000K | 16" | 5" | 3"

LED **DIM** **ADA** **3in1** color temperature
 3000K/3500K/4000K





Satin Nickel/
White Linen

TORY

- Die-cast metal arms
- White linen (WH) or linen acrylic (LA) shade
- White acrylic top and bottom diffuser

LED


- 120-277V universal-voltage driver
- Compatible with residential (TRIAC/ELV) and commercial (0-10V) dimmers
- TRIAC and ELV dimming only at 120V
- 50,000 hr. LED life, 90 CRI
- Adjustable CCT

Single Arm

Satin Nickel		Oakley Bronze		LED	Source Lumens	Adjustable CCT	H	W	D
TYS062307LAJUDSNWH		TYS062307LAJUDKBWH		9W	700	3000K/3500K/4000K	22-3/4"	5-5/8"	4"
TYS062307LAJUDSNLA		TYS062307LAJUDKBLA		9W	700	3000K/3500K/4000K	22-3/4"	5-5/8"	4"

Double Arm

Satin Nickel		Oakley Bronze		LED	Source Lumens	Adjustable CCT	H	W	D
TYS112314LAJUDSNWH		TYS112314LAJUDKBWH		17W	1400	3000K/3500K/4000K	22-3/4"	11-3/8"	4"
TYS112314LAJUDSNLA		TYS112314LAJUDKBKLA		17W	1400	3000K/3500K/4000K	22-3/4"	11-3/8"	4"





SCONCE

Oakley Bronze/Linen Acrylic Topy Shown



Satin Nickel/
Linen Acrylic



Champagne/
Cream Linen

SHERIDAN

- Single or double die-cast metal arm
- Linen acrylic (LA) shade with satin nickel finish or cream linen (LN) shade with champagne finish

LED


- 120-277V universal-voltage driver
- Compatible with residential (TRIAC/ELV) and commercial (0-10V) dimmers
- 50,000 hr. LED life, 90 CRI
- Adjustable CCT

Single Arm

Satin Nickel	Champagne	LED	Source Lumens	Adjustable CCT	H	W	D
SHS061807LAJUDSNLA	SHS061807LAJUDACLN	9W	700	3000K/3500K/4000K	18-1/2"	6-1/8"	4"

Double Arm

Satin Nickel	Champagne	LED	Source Lumens	Adjustable CCT	H	W	D
SHS121814LAJUDSNLA	SHS121814LAJUDACLN	17W	1400	3000K/3500K/4000K	18"	12-5/8"	4"



Companions







Satin Nickel


NOLAN

- Die-cast metal housing with accents
- Clear outer glass
- White acrylic inner diffuser

LED

- 120-277V universal-voltage driver
- Compatible with residential (TRIAC/ELV) and commercial (0-10V) dimmers
- 50,000 hr. LED life, 90 CRI
- Adjustable CCT

Satin Nickel	Oakley Bronze	LED	Source Lumens	Adjustable CCT	H	W	D
NLS061214LAJUDSN	NLS061214LAJUDKB	17W	1400	3000K/3500K/4000K	12-5/8"	6-1/2"	3-7/8"
NLS061914LAJUDSN	NLS061914LAJUDKB	17W	1400	3000K/3500K/4000K	19-1/2"	6-1/2"	3-7/8"





Oil-Rubbed Bronze



Satin Nickel

MONTROSE

- Single or double die-cast metal arm
- Cream linen shade

LED


- 120V TRIAC dimmable
- 50,000 hr. LED life, 90 CRI
- Adjustable CCT

Single Arm

Satin Nickel	Oil-Rubbed Bronze	LED	Source Lumens	Adjustable CCT	H	W	D
MNS081805LAJD1SN	MNS081805LAJD1RB	7W	500	3000K/3500K/4000K	18-1/8"	7-1/2"	4"

Double Arm

Satin Nickel	Oil-Rubbed Bronze	LED	Source Lumens	Adjustable CCT	H	W	D
MNS131810LAJD1SN	MNS131810LAJD1RB	14W	1000	3000K/3500K/4000K	18-1/8"	12-1/2"	4"





TAYLOR

- Single or double die-cast metal arm
- Linen acrylic shade
- White acrylic top and bottom diffuser

LED


- 120-277V universal-voltage driver
- Compatible with residential (TRIAC/ELV) and commercial (0-10V) dimmers
- 50,000 hr. LED life, 90 CRI
- Adjustable CCT

Single Arm

Polished Chrome	LED	Source Lumens	Adjustable CCT	H	W	D
TAS061307LAJUDPCLA	9W	700	3000K/3500K/4000K	13-1/2"	6-1/8"	4"

Double Arm

Polished Chrome	LED	Source Lumens	Adjustable CCT	H	W	D
TAS131314LAJUDPCLA	17W	1400	3000K/3500K/4000K	13-1/2"	12-5/8"	4"



Companion





Oil-Rubbed Bronze



White

LANCET


- Decorative finials
- White glass diffuser with satin nickel finials or tea-stained glass diffuser with oil-rubbed bronze finials

LED

- 120-277V universal-voltage driver
- Compatible with residential (TRIAC/ELV) and commercial (0-10V) dimmers
- 50,000 hr. LED life, 90 CRI
- Adjustable CCT

White	Oil-Rubbed Bronze	LED	Source Lumens	Adjustable CCT	H	W	D
LCS061514LAJUDWH	LCS061514LAJUDRB	17W	1400	3000K/3500K/4000K	15"	5-7/8"	3-7/8"

LED
DIM
ADA
3in1 color temperature
 3000K/3500K/4000K





Oakley Bronze

ALGIERS

- Metal ends
- Linen acrylic front diffuser
- White acrylic top and bottom diffuser
- Vertical or horizontal mounting

LED

- 120-277V universal-voltage driver
- Compatible with residential (TRIAC/ELV) and commercial (0-10V) dimmers
- 50,000 hr. LED life, 90 CRI
- Adjustable CCT



Satin Nickel

Satin Nickel	Oakley Bronze	LED	Source Lumens	Adjustable CCT	H	W	D
ALS160614LAJUDSN	ALS160614LAJUDKB	17W	1400	3000K/3500K/4000K	6"	15-1/2"	4"

LED
DIM
ADA
3in1 color temperature
 3000K/3500K/4000K



Companions





ARLO

- Metal housing
- Frosted acrylic diffuser

LED

- 120V TRIAC dimmable (D1)
- 120-277V universal voltage, non-dimmable (MV)
- 50,000 hr. LED life, 90 CRI

Satin Nickel	Source			H	W	D
	LED	Lumens	CCT			
ARLS050407L35D1SN	10W	600	3500K	5"	4-5/8"	3-1/2"
*ARLS050407L35MVSN	10W	600	3500K	5"	4-5/8"	3-1/2"



Companion





Satin Nickel



FUSION

- Metal accent trim band
- White textured glass diffuser with open top
- White glass bottom diffuser

LED

- 120-277V universal-voltage driver
- Compatible with residential (TRIAC/ELV) and commercial (0-10V) dimmers
- 50,000 hr. LED life, 90 CRI
- Adjustable CCT




Oil-Rubbed Bronze

Satin Nickel	Oil-Rubbed Bronze	LED	Source Lumens	Adjustable CCT	H	W	D
FUS101114LAJUDSN	FUS101114LAJUDRB	17W	1400	3000K/3500K/4000K	11-1/4"	9-7/8"	4"



3in1^{color}
temperature
3000K/3500K/4000K

Companions





Satin Nickel

BRIO

- Decorative metal bands
- White acrylic diffuser, open top and bottom

LED


- 120-277V universal-voltage driver
- Compatible with residential (TRIAC/ELV) and commercial (0-10V) dimmers
- 50,000 hr. LED life, 90 CRI
- Adjustable CCT

Satin Nickel	Oil-Rubbed Bronze	LED	Source Lumens	Adjustable CCT	H	W	D
BRS071814LAJUDSN	BRS071814LAJUDRB	17W	1400	3000K/3500K/4000K	18"	7-1/4"	4"

LED
DIM
ADA
3in1 color temperature
 3000K/3500K/4000K



Oil-Rubbed Bronze





CENTURY

- Die-cast metal accents
- White glass diffuser

LED


- 120-277V universal-voltage driver
- Compatible with residential (TRIAC/ELV) and commercial (0-10V) dimmers
- 50,000 hr. LED life, 90 CRI
- Adjustable CCT

Polished Chrome	LED	Source Lumens	Adjustable CCT	H	W	D
CES111214LAJUDPC	17W	1400	3000K/3500K/4000K	12"	10-7/8"	4"



3in1 color temperature
3000K/3500K/4000K

Companion





IDEAL

- Metal ends
- White glass diffuser
- White acrylic bottom


LED


- 120-277V universal-voltage driver
- 50,000 hr. LED life, 80 CRI

Satin Nickel	LED	Source Lumens	CCT	H	W	D
IDS09101600L41SN	15W	1300	4000K	10"	8-3/4"	3-1/2"



Companions






PLANE

- White powder coated metal faceplate
- Frosted acrylic diffuser
- Indirect light for wall wash effect
- Wall or ceiling mount

LED

- 120-277V universal-voltage driver
- 0-10V dimming
- 50,000 hr. LED life, 90 CRI

White	LED	Source Lumens	CCT	H	W	D
PLNS090909L30D2WH	16W	960	3000K	9"	9"	2"




ECLIPSE


- White powder coated metal faceplate
- Frosted acrylic diffuser
- Indirect light for wall wash effect
- Wall or ceiling mount

LED

- 120-277V universal-voltage driver
- 0-10V dimming
- 50,000 hr. LED life, 90 CRI

White	LED	Source Lumens	CCT	DIA.	D
ECPS090909L30D2WH	16W	900	3000K	9"	2"





SCONCE



Brushed Nickel

VENTURA

- Decorative metal bands
- White acrylic diffuser
- Open top and bottom

LED

- 120V operation
- 50,000 hr. LED life, 80 CRI

Brushed Nickel	Oil-Rubbed Bronze	LED	Source Lumens	CCT	H	W	D
VNTS071009L30ENBN	VNTS071009L30ENRB	9W	900	3000K	9-7/8"	7-1/8"	3-1/2"



Oil-Rubbed Bronze






DORSET

- Decorative metal accents
- Matte white glass

LED

- 120-277V universal-voltage driver
- 50,000 hr. LED life, 80 CRI

Satin Nickel	LED	Source Lumens	CCT	H	W	D
IDSS09111600L41SN	14W	1300	4000K	11-5/8"	9"	4"



OPUS

- Metal trim band
- Faux alabaster white glass

LED

- 120V operation
- 50,000 hr. LED life, 80 CRI

Brushed Nickel	LED	Source Lumens	CCT	H	W	D
QSSS150712L30ENBN	10.5W	600	3000K	7-1/2"	15"	4"




UNITY

- Decorative finials
- Brushed nickel and oil-rubbed bronze finials included
- White glass diffuser

LED

- 120V operation
- 50,000 hr. LED life, 80 CRI

Brushed Nickel	LED	Source Lumens	CCT	H	W	D
USS080812L30ENBN	10W	1200	3000K	8-1/4"	8"	4"






RADIO CITY

- Metal frame
- White acrylic diffuser

LED

- 120-277V universal-voltage
- 50,000 hr. LED life, 80 CRI

Textured White	LED	Source Lumens	CCT	H	W	D
RDS11101600L41WH	14W	1500	4100K	10-3/4"	11-1/2"	3-5/8"



RETROFIT KITS

- For sconces or ceiling applications
- Easy magnetic mount to back plate
- Linear LED module
- Replaces 18W CFL

LED

- 120-277V universal-voltage
- 50,000 hr. LED life
- Adjustable from 3000K or 4000K CCT, 80 CRI

White	LED	Source Lumens	CCT	L X W (LED Board)
RFKIT13AJ	13W	1350/1400	3000K/4000K	11 x 1-7/16"



- For sconces or ceiling applications
- Easy magnetic mount to back plate
- Half-round LED module
- Replaces 13W CFL

LED

- 120-277V universal-voltage
- 50,000 hr. LED life
- Adjustable from 3000K or 4000K CCT, 80 CRI

White	LED	Source Lumens	CCT	L X W (LED Board)
RFKIT9AJ	9W	930/1000	3000K/4000K	6-5/16" x 2-5/8"



CEILING



Grey Linen

CLARA

- Metal hex frame
- Interchangeable grey linen fabric and white acrylic side diffusers (both included)
- White bottom acrylic diffuser

LED

- 120V TRIAC dimmable
- 50,000 hr. LED life, 90 CRI
- Adjustable CCT

Satin Nickel/Grey	LED	Source Lumens	Adjustable CCT	L	W	D
CLAF1418LAJD1SNGY	20W	1800	3000K/3500K/4000K	16"	13-7/8"	3-3/4"





CEILING





LAMBERT

- Ornamental metal accents
- Grey linen fabric side diffuser
- White bottom acrylic diffuser

LED

- 120-277V universal-voltage driver
- Compatible with residential (TRIAC/ELV) and commercial (0-10V) dimmers
- TRIAC and ELV dimming only at 120V
- 50,000 hr. LED life, 90 CRI
- Adjustable CCT

Satin Nickel/Grey	LED	Source Lumens	Adjustable CCT	DIA.	D
LBTF1624LAJUDSNGY	30W	2400	3000K/3500K/4000K	16"	4"
LBTF2032LAJUDSNGY	42W	3200	3000K/3500K/4000K	20"	4"



3in1 color temperature
 3000K/3500K/4000K





REEVES

- Ornamental metal accents
- White linen fabric side diffuser
- White bottom acrylic diffuser

LED

- 120-277V universal-voltage driver
- Compatible with residential (TRIAC/ELV) and commercial (0-10V) dimmers
- TRIAC and ELV dimming only at 120V
- 50,000 hr. LED life, 90 CRI
- Adjustable CCT

	LED	Source Lumens	Adjustable CCT	DIA.	D
Satin Nickel/Linen White RVEF1624LAJUDSNLW	30W	2400	3000K/3500K/4000K	16"	4"
RVEF2032LAJUDSNLW	42W	3200	3000K/3500K/4000K	20"	4"





CEILING



Black/Gold

ASH

- Metal perforated ring
- Powder coated finish
- White acrylic diffuser

LED

- 120V TRIAC dimmable (D1)
- 120-277V universal-voltage driver, 0-10V dimming (D2)
- 50,000 hr. LED life, 90 CRI



White

Black/Gold	White	LED	Source Lumens	CCT	DIA.	D
ASHF1214L30D1BK	ASHF1214L30D1WH	17.5W	1400	3000K	12"	4"
ASHF1214L30D2BK	ASHF1214L30D2WH	17.5W	1400	3000K	12"	4"
ASHF1626L30D1BK	ASHF1626L30D1WH	31W	2600	3000K	16"	4-1/2"
ASHF1626L30D2BK	ASHF1626L30D2WH	31W	2600	3000K	16"	4-1/2"



Companions





White

BOON

- Metal housing
- Edge-lit light panel
- Low-profile design

LED

- 120V TRIAC dimmable (D1)
- 120-277V universal-voltage driver, 0-10V dimming (D2)
- 50,000 hr. LED life, 90 CRI



Black

White	Black	LED	Source Lumens	CCT	DIA.	D
BOF121400L30D1WH	BOF121400L30D1BK	17.5W	1400	3000K	12"	4"
BOF121400L30D2WH	BOF121400L30D2BK	17.5W	1400	3000K	12"	4"
BOF162600L30D1WH	BOF162600L30D1BK	31W	2600	3000K	16"	4-1/2"
BOF162600L30D2WH	BOF162600L30D2BK	31W	2600	3000K	16"	4-1/2"



Companions







TATUM

- Metal housing
- White acrylic diffuser

LED

- 120V TRIAC dimmable (D1)
- 120-277V universal-voltage driver, 0-10V dimming (D2)
- 50,000 hr. LED life, 90 CRI

Satin Nickel	LED	Source Lumens	CCT	DIA.	D
TTMF1214L30D1SN	17.5W	1400	3000K	12"	2-3/4"
TTMF1214L30D2SN	17.5W	1400	3000K	12"	2-3/4"
TTMF1626L30D1SN	31W	2600	3000K	16"	2-3/4"
TTMF1626L30D2SN	31W	2600	3000K	16"	2-3/4"





Chrome/Black

ALTA

- Metal housing
- Edge-lit light panel
- Low profile design

LED

- 120V TRIAC dimmable (D1)
- 120-277V universal-voltage driver, 0-10V dimming (D2)
- 50,000 hr. LED life, 90 CRI

Black/Chrome	Satin Nickel/White	LED	Source Lumens	CCT	DIA.	D
AAF121400L30D1BKPC	AAF121400L30D1SNWH	17.5W	1400	3000K	12"	2"
AAF121400L30D2BKPC	AAF121400L30D2SNWH	17.5W	1400	3000K	12"	2"
AAF162600L30D1BKPC	AAF162600L30D1SNWH	31W	2600	3000K	16"	2"
AAF162600L30D2BKPC	AAF162600L30D2SNWH	31W	2600	3000K	16"	2"





CEILING



Chrome/Black

REVEAL

- Metal housing
- Edge-lit light panel
- Low profile design

LED

- 120V TRIAC dimmable (D1)
- 120-277V universal-voltage driver, 0-10V dimming (D2)
- 50,000 hr. LED life, 90 CRI



Black/Gold

Black/Gold	White/Black	LED	Source Lumens	CCT	DIA.	D
RVF121400L30D1BKGD	RVF121400L30D1WHBK	17.5W	1400	3000K	12"	2-3/4"
RVF121400L30D2BKGD	RVF121400L30D2WHBK	17.5W	1400	3000K	12"	2-3/4"
RVF162600L30D1BKGD	RVF162600L30D1WHBK	31W	2600	3000K	16"	3-1/4"
RVF162600L30D2BKGD	RVF162600L30D2WHBK	31W	2600	3000K	16"	3-1/4"





LENOX

- White acrylic decorative rings
- White bottom diffuser

LED

- 120V TRIAC dimmable
- 50,000 hr. LED life, 90 CRI
- Adjustable CCT

White	LED	Source Lumens	Adjustable CCT	DIA.	D
LENF1418LAJD1WH	22W	1800	3000K/3500K/4000K	14"	3-1/2"
LENF1725LAJD1WH	33W	2500	3000K/3500K/4000K	16-1/2"	3-1/2"
LENF2332LAJD1WH	46W	3200	3000K/3500K/4000K	23"	3-1/2"



3in1 color temperature
3000K/3500K/4000K





White

PEARSON

- Metal housing
- White acrylic diffuser

LED

- 120-277V universal-voltage driver
- Compatible with residential (TRIAC/ELV) and commercial (0-10V) dimmers
- TRIAC and ELV dimming only at 120V
- 50,000 hr. LED life, 90 CRI
- Adjustable CCT

White	Satin Nickel	LED	Source Lumens	Adjustable CCT	SQ.	D
PEAF1215LAJUDWH	PEAF1215LAJUdsn	15W	1400	2700K/3000K/3500K	12"	3-3/16"
PEAF1624LAJUDWH	PEAF1624LAJUdsn	30W	2400	2700K/3000K/3500K	16"	3-3/16"



3in1 color temperature
2700K/3000K/3500K





CEILING



OCTAVIA

- Painted brushed aluminum trim band
- White acrylic diffuser

LED

- 120V TRIAC dimmable
- 50,000 hr. LED life, 90 CRI
- Adjustable CCT

Brushed Aluminum	LED	Source Lumens	Adjustable CCT	DIA.	D
OTVF1218LAJD1BA	22W	1800	3000K/3500K/4000K	12"	3"
OTVF1425LAJD1BA	33W	2500	3000K/3500K/4000K	14"	3"
OTVF1932LAJD1BA	46W	3200	3000K/3500K/4000K	19"	3"

LED
DIM
ENERGY STAR
T24
3in1 color temperature
 3000K/3500K/4000K





ASHLAND

- Linen fabric
- White bottom acrylic diffuser

LED

- 120V TRIAC dimmable
- 50,000 hr. LED life, 90 CRI
- Adjustable CCT

Grey	LED	Source Lumens	Adjustable CCT	DIA.	D
ALDF1318LAJD1GY	22W	1800	3000K/3500K/4000K	12-1/2"	3-1/2"
ALDF1525LAJD1GY	33W	2500	3000K/3500K/4000K	15"	3-1/2"
ALDF2032LAJD1GY	46W	3200	3000K/3500K/4000K	20"	4-1/2"



3in1 color temperature
3000K/3500K/4000K





SINCLAIR

- Metal housing
- Frosted white acrylic diffuser

LED

- 120-277V universal-voltage driver
- Compatible with residential (TRIAC/ELV) and commercial (0-10V) dimmers
- TRIAC and ELV dimming only at 120V
- 50,000 hr. LED life, 90 CRI
- Adjustable CCT

Satin Nickel	LED	Source Lumens	Adjustable CCT	SQ.	D
SNF141400LAJUDSN	15W	1400	2700K/3000K/3500K	14"	4-1/2"
SNF172400LAJUDSN	30W	2400	2700K/3000K/3500K	17"	4-1/2"



Companions





Satin Nickel

SLOANE

- Extruded metal frame
- Edge-lit light panel
- Low profile

LED

- 120V TRIAC dimmable
- 50,000 hr. LED life, 90 CRI



White

		LED	Source Lumens	CCT	L	W	D
Satin Nickel	White						
SLF12121100L30D1SN	SLF12121100L30D1WH	18.5W	1100	3000K	15"	15"	2"
SLF12241800L30D1SN	SLF12241800L30D1WH	25.8W	1800	3000K	27"	15"	2"



Companion





Satin Nickel

ZURICH

- Extruded metal frame
- Edge-lit light panel
- Low profile

LED

- 120V TRIAC dimmable
- 50,000 hr. LED life, 90 CRI



White

Satin Nickel	White	LED	Source Lumens	CCT	L	W	D
ZUF12121100L30D1SN	ZUF12121100L30D1WH	18.5W	1100	3000K	15"	15"	2-3/8"
ZUF12241800L30D1SN	ZUF12241800L30D1WH	26W	1800	3000K	27"	15"	2-3/8"



Companion





Satin Nickel

ATLAS

- Extruded metal frame
- Edge-lit light panel
- Low profile

LED

- 120V TRIAC dimmable
- 50,000 hr. LED life, 90 CRI



Oil-Rubbed Bronze

Satin Nickel	Oil-Rubbed Bronze	LED	Source Lumens	CCT	L	W	D
ATLF12121100L30D1SN	ATLF12121100L30D1RB	18.5W	1100	3000K	15"	15"	2"
ATLF12241800L30D1SN	ATLF12241800L30D1RB	26W	1800	3000K	27"	15"	2"



Companion





MONTCLAIR

- LumaFuse™ laminated fabric/acrylic shade
- Stepped white acrylic bottom diffuser
- Options: Semi-flush mounting, battery back-up

LED


- 120-277V universal-voltage driver
- Compatible with residential (TRIAC/ELV) and commercial (0-10V) dimmers
- TRIAC and ELV dimming only at 120V
- 50,000 hr. LED life, 90 CRI
- Adjustable CCT



Semi-Flush

Satin Nickel/Black	LED	Source Lumens	Adjustable CCT	DIA.	D
MCF1214LAJUDSN-BK	18W	1400	3000K/3500K/4000K	12-1/4"	3-3/4"
MCF1524LAJUDSN-BK	30W	2400	3000K/3500K/4000K	15"	4-3/4"
MCF1932LAJUDSN-BK	42W	3200	3000K/3500K/4000K	19-1/4"	5-1/2"

LED
DIM
BB†
3in1
color temperature
3000K/3500K/4000K



Companion






ACADIA

- Metal faceted head
- Heads swivel and pivot

LED

- 120V TRIAC dimmable
- 50,000 hr. LED life, 90 CRI

Satin Nickel	LED	Source Lumens	CCT	DIA.	D
ACAF0814L30D1SN	20W	1400	3000K	7-1/2"	5-5/8"



Companion





Espresso/Jute

APEX

- Solid wood accent detail
- LumaFuse™ laminated fabric/acrylic shade
- White bottom acrylic diffuser
- Options: Semi-flush mounting, battery back-up

LED

- 120-277V universal-voltage driver
- Compatible with residential (TRIAC/ELV) and commercial (0-10V) dimmers
- TRIAC and ELV dimming only at 120V
- 50,000 hr. LED life, 90 CRI
- Adjustable CCT



Weathered Gray/
Linen White


Espresso/Jute	Weathered Grey/Jute	LED	Source Lumens	Adjustable CCT	DIA.	D
APF1214LAJUDES-JT	APF1214LAJUDWG-JT	18W	1400	3000K/3500K/4000K	14-1/4"	4-1/4"
APF1524LAJUDES-JT	APF1524LAJUDWG-JT	30W	2400	3000K/3500K/4000K	17"	4-1/4"
APF1932LAJUDES-JT	APF1932LAJUDWG-JT	42W	3200	3000K/3500K/4000K	21-1/4"	4-1/4"



Espresso


Weathered Grey

Espresso/Linen White	Weathered Grey/ Linen White	LED	Source Lumens	Adjustable CCT	DIA.	D
APF1214LAJUDES-LW	APF1214LAJUDWG-LW	18W	1400	3000K/3500K/4000K	14-1/4"	4-1/4"
APF1524LAJUDES-LW	APF1524LAJUDWG-LW	30W	2400	3000K/3500K/4000K	17"	4-1/4"
APF1932LAJUDES-LW	APF1932LAJUDWG-LW	42W	3200	3000K/3500K/4000K	21-1/4"	4-1/4"



Jute

Linen White



Companions





Oakley Bronze
Bronze/White

CORTEZ

- Sheer organza fabric outer shade
- White linen inner shade
- White acrylic bottom diffuser

LED

- 120-277V universal-voltage driver
- Compatible with residential (TRIAC/ELV) and commercial (0-10V) dimmers
- TRIAC and ELV dimming only at 120V
- 50,000 hr. LED life, 90 CRI
- Adjustable CCT



Satin Nickel
White/White

Satin Nickel/White

CZF1824LAJUDSN-WHWH	30W	2400	3000K/3500K/4000K	18"	6-5/8"
CZF2432LAJUDSN-WHWH	42W	3200	3000K/3500K/4000K	24"	6-5/8"
CZF3040LAJUDSN-WHWH	60W	4400	3000K/3500K/4000K	30"	6-5/8"

Satin Nickel/Bronze

CZF1824LAJUDSN-BZWH	30W	2400	3000K/3500K/4000K	18"	6-5/8"
CZF2432LAJUDSN-BZWH	42W	3200	3000K/3500K/4000K	24"	6-5/8"
CZF3040LAJUDSN-BZWH	60W	4400	3000K/3500K/4000K	30"	6-5/8"

LED	Source Lumens	Adjustable CCT	DIA.	D
30W	2400	3000K/3500K/4000K	18"	6-5/8"
42W	3200	3000K/3500K/4000K	24"	6-5/8"
60W	4400	3000K/3500K/4000K	30"	6-5/8"



Oakley Bronze/White

CZF1824LAJUDKB-WHWH	30W	2400	3000K/3500K/4000K	18"	6-5/8"
CZF2432LAJUDKB-WHWH	42W	3200	3000K/3500K/4000K	24"	6-5/8"
CZF3040LAJUDKB-WHWH	60W	4400	3000K/3500K/4000K	30"	6-5/8"

Oakley Bronze/Bronze

CZF1824LAJUDKB-BZWH	30W	2400	3000K/3500K/4000K	18"	6-5/8"
CZF2432LAJUDKB-BZWH	42W	3200	3000K/3500K/4000K	24"	6-5/8"
CZF3040LAJUDKB-BZWH	60W	4400	3000K/3500K/4000K	30"	6-5/8"

LED	Source Lumens	Adjustable CCT	DIA.	D
30W	2400	3000K/3500K/4000K	18"	6-5/8"
42W	3200	3000K/3500K/4000K	24"	6-5/8"
60W	4400	3000K/3500K/4000K	30"	6-5/8"



Oakley
Bronze

Satin
Nickel



Bronze
Shade

White
Shade

Companions





Linen White

SANIBEL

- LumaFuse™ laminated fabric/acrylic shade
- White bottom acrylic inner diffuser
- Options: Semi-flush mounting, battery back-up


LED

- 120-277V universal-voltage driver
- Compatible with residential (TRIAC/ELV) and commercial (0-10V) dimmers
- TRIAC and ELV dimming only at 120V
- 50,000 hr. LED life, 90 CRI
- Adjustable CCT



Jute

		LED	Source Lumens	Adjustable CCT	DIA.	D
Satin Nickel/Jute	Satin Nickel/Linen White	18W	1400	3000K/3500K/4000K	16"	5-5/8"
SAF1614LAJUDSN-JT	SAF1614LAJUDSN-LW	30W	2400	3000K/3500K/4000K	18"	5-5/8"
SAF1824LAJUDSN-JT	SAF1824LAJUDSN-LW	42W	3200	3000K/3500K/4000K	23-1/4"	5-5/8"
SAF2332LAJUDSN-JT	SAF2332LAJUDSN-LW					



Companion





Jute

ANTON

- LumaFuse™ laminated fabric/acrylic shade
- White bottom acrylic diffuser
- Options: Semi-flush mounting, battery back-up



LED

- 120-277V universal-voltage driver
- Compatible with residential (TRIAC/ELV) and commercial (0-10V) dimmers
- TRIAC and ELV dimming only at 120V
- 50,000 hr. LED life, 90 CRI
- Adjustable CCT



Linen White

		Source Lumens		Adjustable CCT		DIA.	D
Satin Nickel/Jute	Satin Nickel/Linen White	LED	Adjustable CCT				
ANF1214LAJUDSN-JT	ANF1214LAJUDSN-LW	18W	1400	3000K/3500K/4000K	12-1/4"	4-3/4"	
ANF1524LAJUDSN-JT	ANF1524LAJUDSN-LW	30W	2400	3000K/3500K/4000K	15"	5-1/2"	
ANF1932LAJUDSN-JT	ANF1932LAJUDSN-LW	42W	3200	3000K/3500K/4000K	19-1/4"	5-1/2"	



Companion



SUTTON

- Metal housing
- White glass diffuser

LED

- 120-277V universal-voltage driver
- Compatible with residential (TRIAC/ELV) and commercial (0-10V) dimmers
- TRIAC and ELV dimming only at 120V
- 50,000 hr. LED life, 90 CRI
- Adjustable CCT

Satin Nickel	LED	Source Lumens	Adjustable CCT	DIA.	D
SUF1514LAJUDSN	18W	1400	3000K/3500K/4000K	14-1/2"	4-1/2"
SUF1824LAJUDSN	30W	2400	3000K/3500K/4000K	17-1/2"	4-3/4"





Brushed Nickel

LIMA

- Die-cast decorative metal accents
- Swirl glass diffuser
- Brushed nickel and bronze clips both included

LED

- 120V TRIAC dimmable
- 50,000 hr. LED life, 80 CRI



Bronze

Brushed Nickel	LED	Source Lumens	CCT	DIA	D
LMAF1217L27D1BN	17W	1700	2700K	12"	4"
LMAF1617L27D1BN	17W	1700	2700K	16"	4-3/4"





DELANY

- Die-cast metal accents
- Faceted white acrylic side diffuser
- White acrylic bottom diffuser


LED

- 120-277V universal-voltage driver
- Compatible with residential (TRIAC/ELV) and commercial (0-10V) dimmers
- TRIAC and ELV dimming only at 120V
- 50,000 hr. LED life, 90 CRI
- Adjustable CCT

Satin Nickel	LED	Source Lumens	Adjustable CCT	DIA.	D
MIDF1624LAJUDSN	30W	2400	3000K/3500K/4000K	16-1/4"	5-3/4"
MIDF2232LAJUDSN	42W	3200	3000K/3500K/4000K	22-1/4"	5-1/2"

LED **DIM** **3in1** color temperature
3000K/3500K/4000K

Companion





MONROE


- Die-cast metal finial
- White acrylic diffuser

LED

- 120-277V universal-voltage driver
- Compatible with residential (TRIAC/ELV) and commercial (0-10V) dimmers
- TRIAC and ELV dimming only at 120V
- 50,000 hr. LED life, 90 CRI
- Adjustable CCT

Satin Nickel	LED	Source Lumens	Adjustable CCT	SQ.	D
MRF1624LAJUDSN	24W	2400	3000K/3500K/4000K	16-1/8"	3-1/4"

LED
DIM
3in1 color temperature
3000K/3500K/4000K





Satin Nickel

SHERIDAN

- White linen acrylic side shade in satin nickel or hardback linen shade in champagne
- White acrylic bottom diffuser

LED

- 120-277V universal-voltage driver
- Compatible with residential (TRIAC/ELV) and commercial (0-10V) dimmers
- TRIAC and ELV dimming only at 120V
- 50,000 hr. LED life, 90 CRI
- Adjustable CCT




Champagne

Satin Nickel	Champagne	LED	Source Lumens	Adjustable CCT	DIA.	D
SHC1624LAJUDSN-LA	SHC1624LAJUDAC	30W	2400	3000K/3500K/4000K	16"	6"
SHC2232LAJUDSN-LA	SHC2232LAJUDAC	42W	3200	3000K/3500K/4000K	22"	6"



Companions





HUDSON


- Ornamental metal housing
- Linen acrylic side and bottom diffusers

LED

- 120-277V universal-voltage driver
- Compatible with residential (TRIAC/ELV) and commercial (0-10V) dimmers
- TRIAC and ELV dimming only at 120V
- 50,000 hr. LED life, 90 CRI
- Adjustable CCT

Satin Nickel	LED	Source Lumens	Adjustable CCT	DIA. D
HZC2232LAJUDSN	42W	3200	3000K/3500K/4000K	22" 6"

LED **DIM** **3in1** color temperature
3000K/3500K/4000K





BILBAO


- Linear aluminum bands
- White glass diffuser

LED

- 120-277V universal-voltage driver
- Compatible with residential (TRIAC/ELV) and commercial (0-10V) dimmers
- TRIAC and ELV dimming only at 120V
- 50,000 hr. LED life, 90 CRI
- Adjustable CCT

Satin Aluminum BBF1314LAJUDSA	LED 18W	Source Lumens 1400	Adjustable CCT 3000K/3500K/4000K	DIA. 13-1/4"	D 5"
---	-------------------	------------------------------	--	------------------------	----------------

LED **DIM** **3in1** color temperature
3000K/3500K/4000K



Companion






FUSION

- Metal trim bands
- White textured glass side diffuser
- Smooth white glass bottom diffuser

LED

- 120-277V universal-voltage driver
- Compatible with residential (TRIAC/ELV) and commercial (0-10V) dimmers
- TRIAC and ELV dimming only at 120V
- 50,000 hr. LED life, 90 CRI
- Adjustable CCT

Satin Nickel	LED	Source Lumens	Adjustable CCT	DIA.	D
FUF1314LAJUDSN	18W	1400	3000K/3500K/4000K	12-1/2"	4-3/4"
FUF1624LAJUDSN	32W	2400	3000K/3500K/4000K	15-1/2"	4-3/4"



Companions





Semi-Flush Mount



Flush Mount

CARLISLE

- Metal trim bands
- White acrylic diffuser
- Option: battery back-up (add BB to end of model #)

LED

- 120-277V universal-voltage driver (MV)
- 120V TRIAC dimmable (D1)
- 50,000 hr. LED life, 90 CRI
- Adjustable CCT

Semi-Flush Mount - 120 TRIAC Dimmable

Satin Nickel	LED	Source Lumens	Adjustable CCT	DIA.	D
CAC121200LAJD1	12W	1200	3000K/3500K/4000K	12"	3-1/2"
CAC142400LAJD1	27W	2400	3000K/3500K/4000K	14"	3-1/2"
CAC243100LAJD1	35W	3100	3000K/3500K/4000K	24"	3-1/2"

Flush Mount - 120V TRIAC Dimmable


Satin Nickel	LED	Source Lumens	Adjustable CCT	DIA.	D
CAF121200LAJD1	12W	1200	3000K/3500K/4000K	12"	3-1/2"
CAF142400LAJD1	27W	2400	3000K/3500K/4000K	14"	3-1/2"
CAF243100LAJD1	35W	3100	3000K/3500K/4000K	24"	3-1/2"

Flush Mount - 120-277 universal-voltage Driver

Satin Nickel	LED	Source Lumens	CCT	DIA.	D
CAF121200L30MV	13W	900	3000K	12"	3-1/2"
CAF141200L30MV	13W	1200	3000K	14"	3-1/2"
CAF142400L30MV	27W	2400	3000K	14"	3-1/2"
CAF182900L30MV	27W	2900	3000K	18"	3-1/2"

LED

LED
DIM
ENERGY STAR
BB+
T24
3in1 color temperature
 3000K/3500K/4000K





CEILING



IDEAL


- Metal trim band
- White acrylic diffuser

LED

- 120-277V universal-voltage ballast
- 50,000 hr. LED life, 80 CRI

Satin Nickel	LED	Source Lumens	CCT	L	W	D
PIDF172900L40MVSN	32W	2900	4000K	32"	17"	4"

LED



Companion





Satin Nickel

COVINA

- Metal trim bands
- White acrylic diffuser


LED

- 120V TRIAC dimmable
- 50,000 hr. LED life, 90 CRI



Oil-Rubbed Bronze

Satin Nickel	Oil-Rubbed Bronze	LED	Source Lumens	CCT	L	W	D
CVF324400L30D1SN	CVF324400L30D1RB	45W	4400	3000K	32-3/8"	17"	4-3/8"



CEILING



White

CAPRI

- Metal trim band
- White acrylic diffuser

LED

- 120V TRIAC dimmable
- 50,000 hr. LED life, 90 CRI
- Adjustable CCT



Brushed Nickel

White	Brushed Nickel	LED	Source Lumens	Adjustable CCT	DIA.	D
CFF111600LAJD1WH	CFF111600LAJD1BN	17W	1600	3000K/3500K/4000K	11"	3"
CFF142400LAJD1WH	CFF142400LAJD1BN	27W	2400	3000K/3500K/4000K	14"	3-7/16"
CFF193100LAJD1WH	CFF193100LAJD1BN	35W	3100	3000K/3500K/4000K	19"	4-3/16"

LED
DIM
T24
3in1 color temperature
3000K/3500K/4000K



CAMDEN

- White acrylic diffuser
- Option: battery back-up (add BB to end of model #)

LED

- 120V TRIAC dimmable
- 50,000 hr. LED life, 90 CRI
- Adjustable CCT*

White	LED	Source Lumens	CCT	DIA.	D
CMF091100L30D1	12W	1100	3000K	9"	3-3/4"

White	LED	Source Lumens	Adjustable CCT	DIA.	D
*CMF111600LAJD1	17W	1600	3000K/3500K/4000K	11"	3-3/4"
*CMF142400LAJD1	27W	2400	3000K/3500K/4000K	14"	3-3/4"
*CMF193100LAJD1	35W	3100	3000K/3500K/4000K	19"	3-3/4"



CEILING



CIRRUS

- White acrylic diffuser
- Option: battery back-up (add BB to end of model #)

LED

- 120V TRIAC dimmable (D1)
- 120-277V universal-voltage driver (MV)
- 50,000 hr. LED life, 90 CRI
- Adjustable CCT*

White	LED	Source Lumens	Adjustable CCT	DIA.	D
*C2F111600LAJD1	17W	1600	3000K/3500K/4000K	11"	3"
*C2F142400LAJD1	27W	2400	3000K/3500K/4000K	14"	3"
*C2F193100LAJD1	35W	3100	3000K/3500K/4000K	19"	3"

LED
DIM
ENERGY STAR
BB†
T24
*3in1 color temperature
 3000K/3500K/4000K

White	LED	Source Lumens	CCT	DIA.	D
C2F141700L30MV	17W	1700	3000K	14"	3"
C2F143400L30MV	34W	3400	3000K	14"	3"

LED





CARTER

- White acrylic diffuser

LED

- 120V TRIAC dimmable
- 50,000 hr. LED life, 90 CRI

White	LED	Source Lumens	CCT	L	W	D
CSF101100L27D1	12W	1100	2700K	10"	10"	2-1/2"
CSF101100L30D1	12W	1100	3000K	10"	10"	2-1/2"
CSF121600L27D1	17W	1600	2700K	12"	12"	2-1/2"
CSF121600L30D1	17W	1600	3000K	12"	12"	2-1/2"
CSF142400L27D1	27W	2400	2700K	14"	14"	2-1/2"
CSF142400L30D1	27W	2400	3000K	14"	14"	2-1/2"
CSF193100L27D1	35W	3100	2700K	19"	14"	2-1/2"
CSF193100L30D1	35W	3100	3000K	19"	14"	2-1/2"





Satin Nickel

EDGE ROUND

- Edge-lit disk light panel
- White acrylic diffuser
- Option battery back-up (add BB to the end of model #)

LED

- 120V TRIAC dimmable
- 50,000 hr. LED life, 90 CRI

Round

Satin Nickel	White	LED	Source Lumens	CCT	DIA.	D
EGRF0609L30DISN	EGRF0609L30D1WH	12W	900	3000K	5-3/8"	3/4"
*EGRF0811L30DISN	*EGRF0811L30D1WH	15W	1125	3000K	8"	3/4"
EGRF1216L30DISN	EGRF1216L30D1WH	22W	1650	3000K	12"	3/4"



White



Accessory Kit




EGRF-RET04
For use in converting
4 in. round ceiling cans



EGRF-RET06
For use in converting
6 in. round ceiling cans



EGRF-BB08
Battery back-up
(8 in. model only)





White

EDGE SQUARE

- Edge-lit disk light panel
- White acrylic diffuser

LED

- 120V TRIAC dimmable
- 50,000 hr. LED life, 90 CRI

Square

Satin Nickel	White	LED	Source Lumens	CCT	SQ.	D
EGSF0407L30D1SN	EGSF0407L30D1WH	10W	750	3000K	4"	3/4"
EGSF0611L30D1SN	EGSF0611L30D1WH	15W	1125	3000K	6"	3/4"
EGSF0913L30D1SN	EGSF0913L30D1WH	18W	1350	3000K	9"	3/4"



Satin Nickel



T24



CEILING

RETROFIT KITS

- For sconces or ceiling applications
- Easy magnetic mount to back plate
- Linear LED module
- Replaces 18W CFL

LED

- 120-277V universal-voltage
- 50,000 hr. LED life
- Adjustable from 3000K or 4000K CCT, 80 CRI

White	LED	Source Lumens	CCT	L X W (LED Board)
RFKIT13AJ	13W	1350/1400	3000K/4000K	11 x 1-7/16



- For sconces or ceiling applications
- Easy magnetic mount to back plate
- Half-round LED module
- Replaces 13W CFL

LED

- 120-277V universal-voltage
- 50,000 hr. LED life
- Adjustable from 3000K or 4000K CCT, 80 CRI

White	LED	Source Lumens	CCT	L X W (LED Board)
RFKIT9AJ	9W	930/1000	3000K/4000K	6-5/16" x 2-5/8"



- For ceiling applications
- Easy magnetic mount to back plate
- Round LED module
- Replaces 22W or 32W circline

LED

- 120V operation
- 50,000 hr. LED life
- Adjustable from 3000K or 4000K CCT, 80 CRI

White	LED	Source Lumens	CCT	DIA. (LED Board)
RFKIT22AJ	13W	1200/1300	3000K/4000K	6-5/16"
RFKIT32AJ	17W	1600/1700	3000K/4000K	6-5/16"



- For ceiling applications
- Easy magnetic mount to back plate
- Dual half-round LED module
- Replaces 26W CFL

LED

- 120-277V universal-voltage
- 50,000 hr. LED life
- Adjustable from 3000K or 4000K CCT, 80 CRI

White	LED	Source Lumens	CCT	L X W (LED Board)
RFKIT14AJ	14W	1750/1850	3000K/4000K	6-7/16 x 2-5/8"



VANITY





RYLAND

- Angled metal housing
- White acrylic diffuser
- Edge-lit light panel

LED

- 120-277V universal-voltage driver
- 0-10V dimmable
- 50,000 hr. LED life, 90 CRI

Satin Nickel	LED	Source Lumens	CCT	L	H	D
RYDV280422L30D2SN	26W	2200	3000K	28"	4"	3-1/2"
RYDV380436L30D2SN	38W	3600	3000K	38"	4"	3-1/2"





White

BOON

- Laser cut metal housing
- Low-profile design

LED

- 120V operation
- 50,000 hr. LED life, 90 CRI



Satin Nickel

		White	LED	Source Lumens	CCT	L	H	D
Satin Nickel	BONV240520L30ENSN	BONV240520L30ENWH	30W	2000	3000K	24"	5"	3-1/4"
	BONV360530L30ENSN	BONV360530L30ENWH	30W	3000	3000K	36"	5"	3-1/4"



Companions





Satin Nickel/
Linen White

AVANTI

- Plated metal end caps
- LumaFuse™ laminated fabric/acrylic shade
- Horizontal or vertical mounting

LED

- 120V TRIAC dimmable
- 50,000 hr. LED life, 90 CRI



Oil-Rubbed Bronze/Jute

Satin Nickel/Linen White	Oil-Rubbed Bronze/Jute	LED	Source Lumens	CCT	L	H	D
ATV240520L30DISNLW	ATV240520L30DIRBJT	26W	2000	3000K	27-1/2"	5"	2"
ATV360530L30DISNLW	ATV360530L30DIRBJT	35W	3000	3000K	39-1/2"	5"	2"
ATV480540L30DISNLW	ATV480540L30DIRBJT	49W	4000	3000K	51-1/2"	5"	2"

LED **DIM** **ADA**



Jute



Linen White





Espresso/Jute

APEX

- Solid wood accent detail
- LumaFuse™ laminated fabric/acrylic shade
- White acrylic bottom and top diffuser
- Horizontal or vertical mounting

LED

- 120-277V universal-voltage driver, 0-10V dimming
- 50,000 hr. LED life, 90 CRI
- Adjustable CCT



Weathered Grey/
Linen White

Espresso/Jute		Weathered Grey/Jute		LED	Source Lumens	Adjustable CCT	L	H	D
APV270520LAJD2ES-JT	APV270520LAJD2WG-JT	26W	2000	3000K/3500K/4000K	26-1/2"	4-1/4"	4"		
APV390530LAJD2ES-JT	APV390530LAJD2WG-JT	35W	3000	3000K/3500K/4000K	38-1/2"	4-1/4"	4"		
APV510540LAJD2ES-JT	APV510540LAJD2WG-JT	49W	4000	3000K/3500K/4000K	50-1/2"	4-1/4"	4"		

Espresso/Linen White		Weathered Grey/Linen White		LED	Source Lumens	Adjustable CCT	L	H	D
APV270520LAJD2ES-LW	APV270520LAJD2WG-LW	26W	2000	3000K/3500K/4000K	26-1/2"	4-1/4"	4"		
APV390530LAJD2ES-LW	APV390530LAJD2WG-LW	35W	3000	3000K/3500K/4000K	38-1/2"	4-1/4"	4"		
APV510540LAJD2ES-LW	APV510540LAJD2WG-LW	49W	4000	3000K/3500K/4000K	50-1/2"	4-1/4"	4"		

LED **DIM** **ADA** **3in1** color temperature
3000K/3500K/4000K



Companions





Satin Nickel

ALLEN

- Metal trim ends
- Linen acrylic diffuser
- White acrylic bottom diffuser
- Horizontal or vertical mounting

LED

- 120-277V universal-voltage driver, 0-10V dimming
- 50,000 hr. LED life, 90 CRI
- Adjustable CCT



Oil-Rubbed Bronze

		LED	Source Lumens	Adjustable CCT	L	H	D
Satin Nickel	Oil-Rubbed Bronze						
ALNV280520LAJD2SN	ALNV280520LAJD2RB	26W	2000	3000K/3500K/4000K	29-1/2"	4-1/2"	3-3/4"
ALNV400530LAJD2SN	ALNV400530LAJD2RB	35W	3000	3000K/3500K/4000K	41-1/2"	4-1/2"	3-3/4"
ALNV540540LAJD2SN	ALNV540540LAJD2RB	49W	4000	3000K/3500K/4000K	53-1/2"	4-1/2"	3-3/4"



Companion







VANITY

ROWAN

- Metal housing
- Powder coat finish
- White acrylic diffuser
- Horizontal or vertical mounting

LED

- 120-277V universal-voltage driver, 0-10V dimming
- 50,000 hr. LED life, 90 CRI

Satin Nickel		White	LED	Source Lumens	CCT	H	W	D
RWNS180414L30D2SN	RWNS180414L30D2WH	RWNS180414L30D2WH	16W	1400	3000K	18"	4"	2-1/2"
RWNS300424L30D2SN	RWNS300424L30D2WH	RWNS300424L30D2WH	28W	2400	3000K	30"	4"	2-1/2"

Satin Nickel





ARLO

- Metal housing
- Frosted acrylic edge-lit diffusers

LED

- 120V TRIAC dimmable (D1)
- 120-277V universal-voltage non-dimmable (MV)
- 50,000 hr. LED life, 90 CRI



Satin Nickel	LED	Source Lumens	CCT	L	H	D
ARLV250418L35D1SN (3-Light)	30W	1800	3500K	25"	4"	3-3/4"
*ARLV250418L35MVSN (3-Light)	30W	1800	3500K	25"	4"	3-3/4"
ARLV330424L35D1SN (4-Light)	40W	2400	3500K	33"	4"	3-3/4"
*ARLV330424L35MVSN (4-Light)	40W	2400	3500K	33"	4"	3-3/4"





Satin Nickel

ARDEN

- Walnut finish
- Clear outer glass cylinder
- White inner glass cylinder
- Mount up or down

LED


- 120V TRIAC dimmable
- 50,000 hr. LED life, 90 CRI



Oil-Rubbed Bronze

		Source Lumens			L	H	D
Satin Nickel	Oil-Rubbed Bronze	LED	Source Lumens	CCT	L	H	D
RNV15081200L30D1SN	RNV15081200L30D1RB	15.5W	1200	3000K	15-1/2"	8-3/8"	4"
RNV24081800L30D1SN	RNV24081800L30D1RB	22.5W	1800	3000K	23-3/4"	8-3/8"	4"
RNV30082400L30D1SN	RNV30082400L30D1RB	30W	2400	3000K	30"	8-3/8"	4"

LED **DIM** **ADA**



Companion





NOVARA

- Metal accents
- White acrylic diffuser
- Horizontal or vertical mounting

LED

- 120V TRIAC dimmable
- 50,000 hr. LED life, 90 CRI

Satin Nickel	LED	Source Lumens	CCT	L	H	D
NVV5252400L30D1SN	31W	2400	3000K	25"	4-1/2"	3-5/8"
NVV5373600L30D1SN	46.5W	3600	3000K	37"	4-1/2"	3-5/8"
NVV5494800L30D1SN	62W	4800	3000K	49"	4-1/2"	3-5/8"



Companion





VANITY



White

FULTON

- Fabricated metal housing
- Frosted white glass diffuser
- Powder coated finish
- Horizontal or vertical mounting

LED

- 120V TRIAC dimmable
- 50,000 hr. LED life, 90 CRI

White	Black	LED	Source Lumens	CCT	L	H	D
FTS4141200L30D1WH	FTS4141200L30D1BK	15.5W	1200	3000K	13-1/2"	4"	3-1/2"
FTS4241800L30D1WH	FTS4241800L30D1BK	23W	1800	3000K	24"	4"	3-1/2"





VANITY



Satin Nickel

ARIA

- Die-cast aluminum ends
- White acrylic diffuser
- Horizontal or vertical mounting



Oil-Rubbed Bronze

LED

- 120-277V universal-voltage driver
- 50,000 hr. LED life, 90 CRI

		Source					
		LED	Lumens	CCT	L	H	D
Satin Nickel	Oil-Rubbed Bronze						
ARV26041000L30MVSN	ARV26041000L30MVRB	20W	1000	3000K	26-1/4"	4"	4"
ARV38041400L30MVSN	ARV38041400L30MVRB	30W	1400	3000K	38"	4"	4"
ARV50042100L30MVSN	ARV50042100L30MVRB	40W	2100	3000K	50"	4"	4"





Satin Nickel

CHARLOTTE

- Perforated metal ends
- White acrylic diffuser
- Horizontal or vertical mounting

LED

- 120-277V universal-voltage, 0-10V dimming
- 50,000 hr. LED life, 90 CRI
- Adjustable CCT



Oil-Rubbed Bronze

		LED	Source Lumens	Adjustable CCT	L	H	D
Satin Nickel	Oil-Rubbed Bronze	26W	2000	3000K/3500K/4000K	29-1/4"	4-1/2"	3-3/8"
CHV290520LAJD2SN	CHV290520LAJD2RB	35W	3000	3000K/3500K/4000K	41-1/4"	4-1/2"	3-3/8"
CHV410530LAJD2SN	CHV410530LAJD2RB						



Companion





ALGIERS

- Metal ends
- Linen acrylic front diffuser
- White acrylic top and bottom diffuser
- Horizontal or vertical mounting



Oakley Bronze

LED

- 120-277V universal-voltage, 0-10V dimming
- 50,000 hr. LED life, 90 CRI
- Adjustable CCT

		LED	Source Lumens	Adjustable CCT	L	H	D
Satin Nickel	Oakley Bronze						
*ALV250520LAJD2SN	*ALV250520LAJD2KB	25W	2000	3000K/3500K/4000K	25-1/4"	5"	4"
*ALV370530LAJD2SN	*ALV370530LAJD2KB	36W	3000	3000K/3500K/4000K	37-1/4"	5"	4"
ALV490540LAJD2SN	ALV490540LAJD2KB	49W	4000	3000K/3500K/4000K	49-1/4"	5"	4-7/8"



Companions





VANITY



FUSION

- Die-cast metal ends and center accent
- White textured glass diffuser
- Horizontal or vertical mounting

LED

- 120-277V universal-voltage, 0-10V dimming
- 50,000 hr. LED life, 90 CRI
- Adjustable CCT



2 ft.

Satin Nickel	LED	Source Lumens	Adjustable CCT	L	H	D
FUV250520LAJD2SN	26W	2000	3000K/3500K/4000K	25-3/4"	5-3/8"	4-3/8"
FUV380530LAJD2SN	35W	3000	3000K/3500K/4000K	37-3/4"	5-3/8"	4-3/8"
FUV500540LAJD2SN	49W	4000	3000K/3500K/4000K	50"	5-3/8"	4-3/8"



Companions





CENTURY

- Die-cast metal accents
- White acrylic diffuser
- Horizontal or vertical mounting

LED

- 120-277V universal-voltage, 0-10V dimming
- 50,000 hr. LED life, 90 CRI
- Adjustable CCT

Polished Chrome	LED	Source Lumens	Adjustable CCT	L	H	D
CEV260420LAJD2PC	26W	2000	3000K/3500K/4000K	26-1/4"	6-1/4"	4-3/8"
CEV380430LAJD2PC	35W	3000	3000K/3500K/4000K	38-1/8"	6-1/4"	4-3/8"
CEV500440LAJD2PC	49W	4000	3000K/3500K/4000K	50"	6-1/4"	4-3/8"



Companion






RIO

- Metal housing
- Double white acrylic diffuser
- Horizontal or vertical mounting

LED


- 120V TRIAC dimmable
- 50,000 hr. LED life, 90 CRI

Satin Nickel	LED	Source Lumens	CCT	L	H	D
RIS321600L30D1SN	16W	1600	3000K	32-1/2"	4"	3-5/8"



Companion





SINCLAIR

- Metal housing
- Frosted white acrylic diffuser
- Horizontal or vertical mounting

LED

- 120-277V universal-voltage, 0-10V dimming
- 50,000 hr. LED life, 90 CRI
- Adjustable CCT

Satin Nickel	LED	Source Lumens	Adjustable CCT	L	H	D
SNV240520LAJD2SN	26W	2000	3000K/3500K/4000K	27"	4-5/8"	3"
SNV360530LAJD2SN	35W	3000	3000K/3500K/4000K	39"	4-5/8"	3"
SNV480540LAJD2SN	49W	4000	3000K/3500K/4000K	50-1/4"	4-5/8"	3"



Companions





BILBAO

- Aluminum bands
- White acrylic diffuser

LED

- 120-277V universal-voltage, 0-10V dimming
- 50,000 hr. LED life, 90 CRI
- Adjustable CCT

Satin Aluminum	LED	Source Lumens	Adjustable CCT	L	H	D
BBV320520LAJD2SA	26W	2000	3000K/3500K/4000K	32-3/8"	4-1/2"	4-1/2"
BBV440530LAJD2SA	35W	3000	3000K/3500K/4000K	44-3/8"	4-1/2"	4-1/2"



Companion





VERNON

- Metal backplate
- White glass diffusers
- Mount up or down


LED

- 120V medium base socket
- 9W LED bulb included
- 50,000 hr. LED life, 90 CRI

Satin Nickel	LED	Source Lumens	CCT	L	H	D
VNV170524L27MBSN (3-Light)	27W	2400	2700K	17-1/2"	8"	5"
VNV290540L27MBSN (5-Light)	45W	4000	2700K	29-1/2"	8"	5"



LED





HOLLYWOOD


- Metal housing
- White diffusers
- Horizontal or vertical mounting

LED

- 120V operation
- 50,000 hr. LED life, 90 CRI



Satin Nickel	LED	Source Lumens	CCT	L	H	D
HLWV240417L30ENSN (3-Light)	20W	1700	3000K	24"	4-3/4"	3-5/8"
HLWV240422L30ENSN (4-Light)	28W	2200	3000K	24"	4-3/4"	3-5/8"





PACIFIC

- Metal ends
- White acrylic diffuser
- Horizontal or vertical mounting

LED

- 120V operation
- 50,000 hr. LED life, 80 CRI

Satin Nickel	LED	Source Lumens	CCT	L	H	D
PCV241700L30SN	17W	1700	3000K	24"	6"	3-1/8"
PCV362500L30SN	25W	2500	3000K	36"	6"	3-1/8"
PCV483400L30SN	34W	3400	3000K	48"	6"	3-1/8"

LED **ADA**





STRATUS

- White acrylic diffuser fully encloses housing
- Horizontal or vertical mounting

LED

- 120-277V universal-voltage, 0-10V dimming
- 50,000 hr. LED life, 90 CRI
- Adjustable CCT

White	LED	Source Lumens	Adjustable CCT	L	H	D
V8PN260420LAJD2WH	26W	2000	3000K/3500K/4000K	26-3/4"	4-5/8"	4"
V8PN380430LAJD2WH	35W	3000	3000K/3500K/4000K	38-3/4"	4-5/8"	4"



FIXED RAIL






DISTRICT

- Clear outer glass
- White glass inner diffuser
- Heads swivel and pivot
- Ceiling or wall mount

LED

- 120V TRIAC dimmable
- 50,000 hr. LED life, 90 CRI

Satin Nickel	LED	Source Lumens	CCT	L	W	H
DISF4400L30SN	25W	1600	3000K	36-1/2"	5-3/8"	7-7/8"





CHAPPELLE


- Heads swivel and pivot
- Ceiling or wall mount

LED

- 120V TRIAC dimmable
- 50,000 hr. LED life, 90 CRI



Satin Nickel	LED	Source Lumens	CCT	L	W	H
CHRF4400L30SN	25W	1600	3000K	36-5/8"	5-1/4"	7"





FIXED RAIL



METRO


- Frosted glass diffusers
- Heads swivel and pivot
- Ceiling or wall mount

LED

- 120V TRIAC dimmable
- 50,000 hr. LED life, 90 CRI



Satin Nickel	LED	Source Lumens	CCT	L	W	H
MTRF4400L30SN	25W	1600	3000K	36-5/8"	5-15/16"	6-13/16"





CORE

- Heads swivel and pivot
- Ceiling or wall mount

LED

- 120V TRIAC dimmable
- 50,000 hr. LED life, 90 CRI


Satin Nickel	LED	Source Lumens	CCT	L	W	H
CRRF4400L30SN	25W	1600	3000K	36-3/8"	5-3/8"	6-1/4"
CRRF6400L30SN	42W	2400	3000K	55-1/8"	5-1/4"	7-1/2"

Polished Chrome	LED	Source Lumens	CCT	L	W	H
CRRF4400L30PC	25W	1600	3000K	36-3/8"	5-3/8"	6-1/4"



Polished Chrome

Satin Nickel



FIXED RAIL






GRAMERCY

- Two-tone finish
- Heads swivel and pivot
- Ceiling or wall mount

LED

- 120V TRIAC dimmable
- 50,000 hr. LED life, 90 CRI

Satin Nickel	LED	Source Lumens	CCT	L	W	H
GRAF4400L30WH	25W	1600	3000K	36-1/2"	5-3/8"	7-7/8"





CANTRELL


- Heads swivel and pivot
- Ceiling or wall mount

LED

- 120V TRIAC dimmable
- 50,000 hr. LED life, 90 CRI



Satin Nickel	LED	Source Lumens	CCT	L	W	H
CARF4400L30SN	25W	1600	3000K	36-5/8"	5-1/4"	5-5/8"





ACADIA


- Heads swivel and pivot
- Ceiling or wall mount

LED

- 120V TRIAC dimmable
- 50,000 hr. LED life, 90 CRI



Satin Nickel	LED	Source Lumens	CCT	L	W	H
ACAF300519L30D1SN	30W	1800	3000K	29-3/4"	6-1/4"	4-1/2"



Companion






SATELLITE

- Heads swivel and pivot
- Ceiling or wall mount

LED

- 120V TRIAC dimmable
- 50,000 hr. LED life, 90 CRI

Satin Nickel	LED	Source Lumens	CCT	L	W	H
STLF4450L30SN	30W	1800	3000K	34-15/16"	5-1/4"	8-1/2"






BERLIN

- Heads swivel and pivot
- Ceiling or wall mount

LED

- 120V TRIAC dimmable
- 50,000 hr. LED life, 90 CRI

Satin Nickel	LED	Source Lumens	CCT	L	W	H
BERF4450L30SN	27W	1800	3000K	36-5/8"	5-7/8"	10-1/2"






MADRID

- Heads swivel and pivot
- Ceiling or wall mount

LED

- 120V TRIAC dimmable
- 50,000 hr. LED life, 90 CRI

Satin Nickel	Oil-Rubbed Bronze	LED	Source Lumens	CCT	DIA.	H
MDRF1213L30SN	MDRF1213L30RB	21W	1300	3000K	11-3/4"	7"



OUTDOOR



ROWAN

- Metal housing
- Durable powder coat finish for outdoor applications
- White acrylic diffuser

LED

- Minimum starting temp -20°F
- 120-277V universal-voltage driver, 0-10V dimmable
- 50,000 hr. LED life, 90 CRI
- Adjustable CCT

	LED	Source Lumens	Adjustable CCT	H	W	D
*RWNW052020LAJD2TG	22W	2000	3000K/3500K/4000K	20"	5"	3-3/8"
RWNW073640LAJD2TG	42W	4000	3000K/3500K/4000K	36"	7"	4-3/8"

	LED	Source Lumens	Adjustable CCT	H	W	D
*RWNW052020LAJD2BZ	22W	2000	3000K/3500K/4000K	20"	5"	3-3/8"
RWNW073640LAJD2BZ	42W	4000	3000K/3500K/4000K	36"	7"	4-3/8"



Textured Grey

OUTDOOR



12" Textured Bronze

AVENUE

- Metal housing
- Durable powder coat finish for outdoor applications
- White acrylic diffuser
- Ceiling or wall mount

LED

- Minimum starting temp -20°F
- 120-277V universal-voltage driver, 0-10V dimmable
- 50,000 hr. LED life, 90 CRI
- Adjustable CCT



8" Textured Grey

Textured Grey	LED	Source Lumens	Adjustable CCT	SQ.	H
AUF0816LAJD2TG	21W	1600	3000K/3500K/4000K	8"	3-3/4"
AUF1228LAJD2TG	21W	1600	3000K/3500K/4000K	12"	3-3/4"

Textured Bronze	LED	Source Lumens	Adjustable CCT	SQ.	H
AUF0816LAJD2BZ	29W	2800	3000K/3500K/4000K	8"	3-3/4"
AUF1228LAJD2BZ	29W	2800	3000K/3500K/4000K	12"	3-3/4"

LED
DIM
WET
3in1 color temperature
 3000K/3500K/4000K

Companion





12" Textured Bronze

BEAUMONT


- Metal housing
- Durable powder coat finish for outdoor applications
- White acrylic diffuser
- Ceiling or wall mount

LED

- Minimum starting temp -20°F
- 120-277V universal-voltage driver, 0-10V dimmable
- 50,000 hr. LED life, 90 CRI
- Adjustable CCT


Textured Grey	LED	Source Lumens	Adjustable CCT	DIA.	H
BMF0816LAJD2TG	21W	1600	3000K/3500K/4000K	8"	3-3/4"
BMF1228LAJD2TG	21W	1600	3000K/3500K/4000K	12"	3-3/4"

Textured Bronze	LED	Source Lumens	Adjustable CCT	DIA.	H
BMF0816LAJD2BZ	29W	2800	3000K/3500K/4000K	8"	3-3/4"
BMF1228LAJD2BZ	29W	2800	3000K/3500K/4000K	12"	3-3/4"



8" Textured Grey

OUTDOOR



Companion







Black



White

BOON

- Metal cut housing
- Durable powder coat finish for outdoor applications
- Frosted glass diffuser
- Down-light illumination

LED

- Minimum starting temp -20°F
- 120-277V universal-voltage driver, 0-10V dimmable
- 50,000 hr. LED life, 90 CRI

White	Black	LED	Source Lumens	CCT	H	W	D
BONW071710L30D2WH	BONW071710L30D2BK	12W	1000	3000K	16"	6"	3"



Companions



OUTDOOR



White

CONCORD

- Metal housing
- Durable powder coat finish for outdoor applications
- Frosted glass diffuser
- Down-light illumination

LED

- Minimum starting temp -20°F
- 120-277V universal-voltage driver, 0-10V dimmable
- 50,000 hr. LED life, 90 CRI

White	Black	LED	Source Lumens	CCT	H	W	D
CNCW100510L30D2WH	CNCW100510L30D2BK	12W	1000	3000K	4-1/2"	10-1/2"	4"





OUTDOOR



Textured Grey



Textured Bronze


LASALLE

- Metal housing
- Durable powder coat finish for outdoor applications
- White acrylic diffuser

LED

- Minimum starting temp -20°F
- 120-277V universal-voltage driver, 0-10V dimmable
- 50,000 hr. LED life, 90 CRI
- Adjustable CCT

Textured Grey		Textured Bronze		LED	Source Lumens	Adjustable CCT	H	W	D
LASW051728LAJD2TG	LASW051728LAJD2BZ	24W	2800	3000K/3500K/4000K	17"	5-1/2"	3-3/8"		
LASW052833LAJD2TG	LASW052833LAJD2BZ	28W	3300	3000K/3500K/4000K	28"	5-1/2"	4"		





Black



White


KNOX

- Metal multi-faceted housing
- Durable powder coat finish for outdoor applications
- Recessed frosted glass diffuser
- Down-light illumination

LED

- Minimum starting temp -20°F
- 120-277V universal-voltage driver, 0-10V dimmable
- 50,000 hr. LED life, 90 CRI

Bronze	White	LED	Source Lumens	CCT	H	W	D
KNXW061010L30D2BZ	KNXW061010L30D2WH	12W	1000	3000K	10"	6-1/4"	3-1/2"



OUTDOOR



White



Black

COLTON

- Metal housing
- Durable powder coat finish for outdoor applications
- Frosted glass diffuser
- Down-light illumination

LED

- Minimum starting temp -20°F
- 120-277V universal-voltage driver, 0-10V dimmable
- 50,000 hr. LED life, 90 CRI

White	Black	LED	Source Lumens	CCT	H	W	D
CLTW060410L30D2WH	CLTW060410L30D2BK	12W	1000	3000K	4-1/4"	6-1/2"	2-1/2"





Black



White


DAKOTA

- Metal housing
- Durable powder coat finish for outdoor applications
- Frosted glass diffuser
- Down-light illumination

LED

- Minimum starting temp -20°F
- 120-277V universal-voltage driver, 0-10V dimmable
- 50,000 hr. LED life, 90 CRI

White	Black	LED	Source Lumens	CCT	H	W	D
DKTW050410L30D2WH	DKTW050410L30D2BK	12W	1000	3000K	4-1/8"	4-7/8"	2-1/2"



OUTDOOR





OUTDOOR

PASADENA

- Tapered metal housing
- Durable powder coat finish for outdoor applications
- White acrylic diffuser

LED

- Minimum starting temp -20°F
- 120-277V universal-voltage driver, 0-10V dimmable
- 50,000 hr. LED life, 90 CRI
- Adjustable CCT

Textured Grey

Textured Grey	LED	Source Lumens	Adjustable CCT	H	W	D
PSDW071223LAJD2TG	20W	2300	3000K/3500K/4000K	12"	6"	3-3/4"
PSDW071833LAJD2TG	28W	3300	3000K/3500K/4000K	18"	6-3/4"	4"

Textured Bronze	LED	Source Lumens	Adjustable CCT	H	W	D
PSDW071223LAJD2BZ	20W	2300	3000K/3500K/4000K	12"	6"	3-3/4"
PSDW071833LAJD2BZ	28W	3300	3000K/3500K/4000K	18"	6-3/4"	4"



3in1 color temperature
3000K/3500K/4000K





Textured Grey



Textured Bronze

BROADWAY


- Metal housing
- Durable powder coat finish for outdoor applications
- White acrylic diffuser

LED

- Minimum starting temp -20°F
- 120-277V universal-voltage driver, 0-10V dimmable
- 50,000 hr. LED life, 90 CRI
- Adjustable CCT

Textured Grey	Source			H	W	D
	LED	Lumens	Adjustable CCT			
*BDWW041423LAJD2TG	20W	2300	3000K/3500K/4000K	13-1/2"	4-1/2"	3"
*BDWW072033LAJD2TG	28W	3300	3000K/3500K/4000K	19-1/2"	6-1/2"	4"
BDWW083035LAJD2TG	36W	3500	3000K/3500K/4000K	30"	8"	5"

Textured Bronze	Source			H	W	D
	LED	Lumens	Adjustable CCT			
*BDWW041423LAJD2BZ	20W	2300	3000K/3500K/4000K	13-1/2"	4-1/2"	3"
*BDWW072033LAJD2BZ	28W	3300	3000K/3500K/4000K	19-1/2"	6-1/2"	4"
BDWW083035LAJD2BZ	36W	3500	3000K/3500K/4000K	30"	8"	5"





Textured
Bronze

PAXTON

- Metal housing
- Durable powder coat finish for outdoor applications
- White acrylic diffuser

LED

- Minimum starting temp -20°F
- 120-277V universal-voltage driver, 0-10V dimmable
- 50,000 hr. LED life, 90 CRI
- Adjustable CCT

	LED	Source Lumens	Adjustable CCT	H	W	D
Textured Grey						
PAXW071223LAJD2TG	20W	2300	3000K/3500K/4000K	12"	7"	3-1/2"
PAXW071828LAJD2TG	24W	2800	3000K/3500K/4000K	18"	7"	3-1/2"

	LED	Source Lumens	Adjustable CCT	H	W	D
Textured Bronze						
PAXW071223LAJD2BZ	20W	2300	3000K/3500K/4000K	12"	7"	3-1/2"
PAXW071828LAJD2BZ	24W	2800	3000K/3500K/4000K	18"	7"	3-1/2"



3in1 color temperature
3000K/3500K/4000K



Textured
Grey

OUTDOOR



Textured Grey

STACK

- Metal housing
- Durable powder coat finish for outdoor applications
- White acrylic diffuser

LED

- Minimum starting temp -20°F
- 120-277V universal-voltage driver, 0-10V dimmable
- 50,000 hr. LED life, 90 CRI
- Adjustable CCT

Textured Grey	LED	Source		H	W	D
		Lumens	Adjustable CCT			
STCW071228LAJD2TG	24W	2800	3000K/3500K/4000K	12"	7"	4"
STCW071833LAJD2TG	28W	3300	3000K/3500K/4000K	18"	7"	4"

Textured Bronze	LED	Source		H	W	D
		Lumens	Adjustable CCT			
STCW071228LAJD2BZ	24W	2800	3000K/3500K/4000K	12"	7"	4"
STCW071833LAJD2BZ	28W	3300	3000K/3500K/4000K	18"	7"	4"





MICHAEL

OUTDOOR

Textured Bronze Stack Shown



Textured Grey



Textured Bronze


BEAUMONT

- Die-cast aluminum housing
- Durable powder coat finish for outdoor applications
- White acrylic diffuser

LED

- Photo cell option (PC)
- Minimum starting temp -20°F
- 120-277V universal-voltage driver, 0-10V dimmable
- 50,000 hr. LED life, 90 CRI

Textured Grey		Textured Bronze		LED	Source Lumens	CCT	H	W	D
BMW5171800L30MVTG		BMW5171800L30MVBZ		19W	1800	3000K	14-3/4"	4-3/4"	4-3/8"
BMW5171800L30MVTG-PC		BMW5171800L30MVBZ-PC		19W	1800	3000K	14-3/4"	4-3/4"	4-3/8"
BMW5212800L30MVTG		BMW5212800L30MVBZ		24W	2800	3000K	21"	4-3/4"	4-1/2"
BMW5212800L30MVTG-PC		BMW5212800L30MVBZ-PC		24W	2800	3000K	21"	4-3/4"	4-1/2"



Companion





Textured Grey



Textured Bronze


BLAINE

- Die-cast aluminum housing
- Durable powder coat finish for outdoor applications
- White acrylic diffuser


LED

- Minimum starting temp -20°F
- 120-277V universal-voltage driver, 0-10V dimmable
- 50,000 hr. LED life, 90 CRI

Textured Grey		Textured Bronze		LED	Source Lumens	CCT	H	W	D
BLW5161800L30MVTG	BLW5161800L30MVBZ	23W	1800	3000K	15-3/4"	4-3/4"	4-1/2"		
BLW5232800L30MVTG	BLW5232800L30MVBZ	28W	2800	3000K	23"	4-3/4"	4-1/2"		



OUTDOOR





LOGAN


Textured Grey

- Die-cast aluminum housing
- Durable powder coat finish for outdoor applications
- Clear seedy glass

LED

- Minimum starting temp -20°F
- 120-277V universal-voltage driver, 0-10V dimmable
- 50,000 hr. LED life, 90 CRI

Textured Grey	Textured Bronze	LED	Source Lumens	CCT	H	W	D
LGW6141800L30MVTG	LGW6141800L30MVBZ	16W	1800	3000K	14"	6-3/8"	4"



OUTDOOR





Textured Grey



Textured Bronze

AVENUE

- Die-cast aluminum housing
- Durable powder coat finish for outdoor applications
- White acrylic diffuser

LED

- Photo cell option (PC)
- Minimum starting temp -20°F
- 120-277V universal-voltage driver, 0-10V dimmable
- 50,000 hr. LED life, 90 CRI
- *Adjustable CCT

Textured Grey		Textured Bronze		LED	Source Lumens	CCT	H	W	D
AUW6122500L30MVTG	AUW6122500L30MVBZ	24W	2500	3000K	12"	5-1/2"	3-1/2"		
AUW6122500L30MVTG-PC	AUW6122500L30MVBZ-PC	24W	2500	3000K	12"	5-1/2"	3-1/2"		
AUW7183200L30MVTG	AUW7183200L30MVBZ	28W	3200	3000K	18"	7"	3-1/2"		
AUW7183200L30MVTG-PC	AUW7183200L30MVBZ-PC	28W	3200	3000K	18"	7"	3-1/2"		

Textured Grey		Textured Bronze		LED	Source Lumens	Adjustable CCT	H	W	D
*AUW103643LAJD2TG	*AUW103643LAJD2BZ	42W	4300	3000K/3500K/4000K	36"	8"	4"		
*AUW103643LAJD2TG-PC	*AUW103643LAJD2BZ-PC	42W	4300	3000K/3500K/4000K	36"	8"	4"		

3000K/3500K/4000K



Companion



OUTDOOR



Textured
Bronze



Textured
Grey

MAX

- Die-cast aluminum housing
- Durable powder coat finish for outdoor applications
- White acrylic diffuser

LED

- Photo sensor option (PC)
- Minimum starting temp -20°F
- 120-277V universal-voltage driver, 0-10V dimmable
- 50,000 hr. LED life, 90 CRI

Textured Grey	LED	Source Lumens	CCT	H	W	D
MXW7122500L30MVTG	24W	2500	3000K	12"	7"	3-3/8"
MXW7122500L30MVTG-PC	24W	2500	3000K	12"	7"	3-3/8"
MXW7183200L30MVTG	29W	3200	3000K	18"	7"	3-3/8"
MXW7183200L30MVTG-PC	29W	3200	3000K	18"	7"	3-3/8"

Textured Bronze	LED	Source Lumens	CCT	H	W	D
MXW7122500L30MVBZ	24W	2500	3000K	12"	7"	3-3/8"
MXW7122500L30MVBZ-PC	24W	2500	3000K	12"	7"	3-3/8"
MXW7183200L30MVBZ	29W	3200	3000K	18"	7"	3-3/8"
MXW7183200L30MVBZ-PC	29W	3200	3000K	18"	7"	3-3/8"





Textured Grey



Textured Bronze

STATE


- Die-cast aluminum housing
- Durable powder coat finish for outdoor applications
- White acrylic diffuser

LED

- Photo sensor option (PC)
- Minimum starting temp -20°F
- 120-277V universal-voltage driver, 0-10V dimmable
- 50,000 hr. LED life, 90 CRI

	LED	Source Lumens	CCT	H	W	D
Textured Grey						
SEW5121500L30MVTG	19W	1500	3000K	12"	4-1/2"	3-1/2"
SEW5121500L30MVTG-PC	19W	1500	3000K	12"	4-1/2"	3-1/2"
SEW5182300L30MVTG	24W	2300	3000K	17"	4-3/4"	3-1/2"
SEW5182300L30MVTG-PC	24W	2300	3000K	17"	4-3/4"	3-1/2"

	LED	Source Lumens	CCT	H	W	D
Textured Bronze						
SEW5121500L30MVBZ	19W	1500	3000K	12"	4-1/2"	3-1/2"
SEW5121500L30MVBZ-PC	19W	1500	3000K	12"	4-1/2"	3-1/2"
SEW5182300L30MVBZ	24W	2300	3000K	17"	4-3/4"	3-1/2"
SEW5182300L30MVBZ-PC	24W	2300	3000K	17"	4-3/4"	3-1/2"



OUTDOOR




BRIO

- Aluminum housing
- Durable powder coat finish for outdoor applications
- White acrylic diffuser

FLUORESCENT

- Photo sensor option (PC)
- Minimum starting temp 0°F
- 120-277V universal-voltage ballast
- CFQ lamps (not included)

Satin Nickel	Oil-Rubbed Bronze	Qty.	Lamp	H	W	D
BRW218SNMV	BRW218RBMV	2	18W CFQ 4-Pin	18"	7-1/4"	4-5/8"
BRW218SNMV-PC	BRW218RBMV-PC	2	18W CFQ 4-Pin	18"	7-1/4"	4-5/8"



Oil-Rubbed Bronze

OUTDOOR




EVERLY

- Metal housing
- Durable powder coat finish for outdoor applications
- Clear acrylic diffuser

LED

- Minimum starting temp -20°F
- 120-277V universal voltage driver
- 50,000 hr. LED life, 90 CRI

Black	LED	Source Lumens	CCT	H	W	D
EVYW070410L30MVBK (1-Light)	12W	1000	3000K	8"	4-1/4"	7"
EVYW070418L30MVBK (2-Light)	24W	1800	3000K	12"	4-1/4"	7"





Black



White


CAPE

- Die-cast aluminum housing with protective guard
- Durable powder coat finish for outdoor applications
- Frosted ribbed glass diffuser

LED

- Minimum starting temp -20°F
- 120V operation
- 50,000 hr. LED life, 90 CRI

White	Black	LED	Source Lumens	CCT	H	W	D
CAPW050804L30ENWH	CAPW050804L30ENBK	6W	430	3000K	8-1/2"	5"	4-3/8"



OUTDOOR

OLDEN

- Aluminum housing
- Frosted glass diffuser

LED

- Minimum starting temp -20°F
- 120V operation
- 50,000 hr. LED life, 80 CRI

Black	LED	Source Lumens	CCT	SQ.	D
OCFW70050LBK	9W	700	5000K	9-1/2"	5-3/8"




DAWSON

- Aluminum housing
- White diffuser
- Integrated photocell for dusk-to-dawn operation

LED

- Minimum starting temp -20°F
- 120V operation
- 50,000 hr. LED life, 80 CRI

Black	LED	Source Lumens	CCT	H	W	D
DWSW300L30BKWGPC	6W	350	3000K	9-1/4"	6-1/8"	6-7/8"



BRISTOL


- Polycarbonate housing
- Frosted polycarbonate diffuser
- Integrated photocell for dusk-to-dawn operation (PC)

LED

- Minimum starting temp -20°F
- 120V operation
- 50,000 hr. LED life, 80 CRI

Black with Photocell	LED	Source Lumens	CCT	H	W	D
BSSW0810700L50BKPC-50	9W	700	5000K	9-1/2"	7-3/4"	4-1/2"

Black	LED	Source Lumens	CCT	H	W	D
BSSW0810700L50BK	9W	700	5000K	9-1/2"	7-3/4"	4-1/2"
White						
BSSW081009L30ENWH	9W	900	3000K	9-1/2"	7-3/4"	4-1/2"




BUTLER

- Aluminum housing
- White glass diffuser

LED

- Minimum starting temp -20°F
- 120V operation
- 50,000 hr. LED life, 80 CRI

Black	LED	Source Lumens	CCT	H	W	D
BTLW061007L30ENBK	9W	830	3000K	10-1/2"	8-3/4"	10-1/2"




PATRIOT

- Aluminum housing
- Frosted glass diffusers
- Integrated photocell for dusk-to-dawn operation

LED

- Minimum starting temp -20°F
- 120V operation
- 50,000 hr. LED life, 80 CRI

Black	LED	Source Lumens	CCT	H	W	D
PSW0812700L50BK	9W	700	5000K	12-1/4"	8"	5"




CLARK

- Aluminum housing
- Clear glass diffusers

LED

- Minimum starting temp -20°F
- 120V operation
- 50,000 hr. LED life, 80 CRI

Black	LED	Source Lumens	CCT	H	W	D
CLKW450L30BK	6W	450	3000K	11-1/2"	6-1/2"	8-1/8"




STRATFORD

- Aluminum housing
- Clear crackle glass
- Integrated photocell for dusk-to-dawn operation

LED

- Minimum starting temp -20°F
- 120V operation
- 50,000 hr. LED life, 80 CRI

Black	LED	Source Lumens	CCT	H	W	D
SATW091508L30ENBK	11W	1100	3000K	15-1/4"	8-1/2"	9-3/4"




NEWPORT

- Aluminum housing
- Frosted glass diffuser

LED

- Minimum starting temp -20°F
- 120V operation
- 50,000 hr. LED life, 80 CRI

Bronze Patina	LED	Source Lumens	CCT	H	W	D
NWPW041409L30ENBP	10W	880	3000K	13-3/4"	4-3/4"	3-1/2"



VENTURA

- Aluminum housing
- White diffuser

LED

- Minimum starting temp -20°F
- 120-277V operation
- 50,000 hr. LED life, 80 CRI

Textured Grey	Oil-Rubbed Bronze	LED	Source Lumens	CCT	H	W	D
VNTW071010L30ENGY	VNTW071010L30ENBZ	9W	1000	3000K	9-7/8"	7-1/8"	3-1/2"



LED WALL PACK

- Die-cast metal housing
- Clear prismatic diffuser

LED

- Minimum starting temp -20°F
- 120V operation
- 50,000 hr. LED life, 80 CRI

Oil-Rubbed Bronze	LED	Source Lumens	CCT	H	W	D
TPWW700L50RB	9W	900	5000K	13-1/4"	4-1/2"	3-3/4"
TPWW1100L50RB	13W	1200	5000K	13-1/4"	4-1/2"	3-3/4"



LED WALL PACK

- Metal housing
- White polycarbonate prismatic diffuser

LED

- Minimum starting temp -20°F
- 120V operation
- 50,000 hr. LED life, 80 CRI

White	LED	Source Lumens	CCT	H	W	D
TPWW70050LWH	9W	900	5000K	14"	5-1/8"	2-3/4"




LED WALL PACK

- Die-cast aluminum housing
- Clear polycarbonate prismatic diffuser

LED

- Minimum starting temp -20°F
- 120V operation
- 50,000 hr. LED life, 80 CRI

White	LED	Source Lumens	CCT	H	W	D
TPUW700L50WH	9W	900	5000K	10-1/2"	6"	4"



OUTDOOR


LED PORCH

- Polycarbonate housing
- Frosted polycarbonate diffuser
- Integrated photocell for dusk-to-dawn operation

LED

- Minimum starting temp -20°F
- 120V residential driver
- 50,000 hr. LED life, 80 CRI

Black	LED	Source Lumens	CCT	H	W	D
BWSW70050LBK	9W	900	5000K	7-1/2"	4-1/2"	5-7/8"




LED WALL PACK

- Aluminum housing
- White polycarbonate diffuser

LED

- Minimum starting temp -20°F
- 120V operation
- 50,000 hr. LED life, 80 CRI

Black	LED	Source Lumens	CCT	H	W	D
WAS08650L30BK	9W	900	3000K	8-3/8"	5-1/8"	2-1/8"




LED FLOOD

- Die-cast aluminum housing with back plate
- Clear polycarbonate prismatic diffuser
- Dusk-to-dawn operation with motion sensor

LED

- Minimum starting temp -20°F
- 120V residential driver
- 50,000 hr. LED life, 80 CRI

Bronze	LED	Source Lumens	CCT	Sensor Range	H	W	D
TPDW1300L50RBMS	14W	1300	5000K	180°	8"	8"	6-1/2"
TPDW2600L50RBMS	29W	2600	5000K	240°	8"	8"	6-1/2"




LED FLOOD

- Die-cast aluminum housing
- Clear polycarbonate prismatic diffuser

LED

- Minimum starting temp -20°F
- 120V residential driver
- 50,000 hr. LED life, 80 CRI

Black	LED	Source Lumens	CCT	H	W	D
TPDW70050LBK	7W	700	5000K	4"	8"	5-7/8"
TPDW1300L50BK	13.5W	1300	5000K	4"	8"	5-7/8"
TPDW2600L50BK	20W	2600	5000K	4"	8"	5-7/8"
TPDW4000L50BK	28W	4000	5000K	4"	8"	5-7/8"



LED UTILITY

- Aluminum housing
- Clear prismatic diffuser
- Integrated photocell for dusk-to-dawn operation

LED

- Minimum starting temp -20°F
- 120V operation
- 50,000 hr. LED life, 80 CRI

White	LED	Source Lumens	CCT	SQ.	D
TPFW70050LWH	9W	900	5000K	10-1/2"	4"
TPFW110050LWH	17W	1700	5000K	10-1/2"	4"




LED SECURITY

- Polycarbonate housing
- Clear acrylic diffuser
- Integrated photocell for dusk-to-dawn operation

LED

- Minimum starting temp -20°F
- 120-277V universal-voltage driver
- 50,000 hr. LED life, 80 CRI

Bronze	LED	Source Lumens	CCT	H	W	D
BWSW060928L50ENRB	26W	2860	5000K	9-1/8"	6"	3-5/8"



OUTDOOR


LED SECURITY

- Polycarbonate housing
- Frosted polycarbonate diffuser
- Integrated photocell for dusk-to-dawn operation

LED

- Minimum starting temp -20°F
- 120V residential driver
- 50,000 hr. LED life, 80 CRI

Bronze	LED	Source Lumens	CCT	H	W	D
BWSW1600L41RB	18W	1800	4100K	10"	7-1/2"	4-3/8"




- Polycarbonate housing
- Frosted polycarbonate diffuser
- Integrated photocell for dusk-to-dawn operation

LED

- Minimum starting temp -20°F
- 120V residential driver
- 50,000 hr. LED life, 80 CRI

Bronze	LED	Source Lumens	CCT	H	W	D
BWSW2400L41RB	27W	2430	4100K	11"	6-3/8"	5-1/2"




- Aluminum housing
- Clear acrylic diffuser
- Integrated photocell for dusk-to-dawn operation

LED

- Minimum starting temp -20°F
- 120V operation
- 50,000 hr. LED life, 80 CRI

Bronze	LED	Source Lumens	CCT	H	W	D
BWSW1400L50RB	12W	1400	5000K	11"	6-7/8"	5-1/4"



OVERBED



Satin Nickel

HAYES

- Wraparound metal frame
- Linen acrylic front diffuser
- White acrylic bottom and top diffuser
- 4-way pull switch with night light

LED

- 120V operation
- 50,000 hr. LED life, 90 CRI



Oil-Rubbed Bronze

Satin Nickel		Oil-Rubbed Bronze	LED	Source Lumens	CCT	L	H	D
HAYB3740L30ENSN		HAYB3740L30ENRB	56W	1350 up/2700 down	3000K	37"	5"	4"
HAYB4954L30ENSN		HAYB4954L30ENRB	68W	1800 up/3600 down	3000K	49"	5"	4"





Satin Nickel

ALLEN

- Decorative metal end caps
- Linen acrylic front diffuser
- White acrylic bottom and top diffuser
- 4-way pull switch with night light

LED

- 120V operation
- 50,000 hr. LED life, 90 CRI




Oil-Rubbed Bronze

Satin Nickel	Oil-Rubbed Bronze	LED	Source Lumens	CCT	L	H	D
ALNB4040L30ENSN	ALNB4040L30ENRB	56W	1350 up/2700 down	3000K	40"	5"	4"
ALNB5254L30ENSN	ALNB5254L30ENRB	68W	1800 up/3600 down	3000K	52"	5"	4"



Companion





Espresso/Jute

APEX

- Solid wood accent
- LumaFuse™ laminated fabric/acrylic shade
- White acrylic bottom and top diffuser
- 4-way pull switch with night light

LED

- 120V operation
- 50,000 hr. LED life, 90 CRI



Weathered Grey/
Linen White

Espresso/Jute	Weathered Grey/Jute	LED	Source Lumens	CCT	L	H	D
APB3940L30ENES-JT	APB3940L30ENWG-JT	56W	1350 up/2700 down	3000K	38"	4-3/8"	4"
APB5154L30ENES-JT	APB5154L30ENWG-JT	68W	1800 up/3600 down	3000K	50"	4-3/8"	4"

Espresso/ Linen White	Weathered Grey/ Linen White	LED	Source Lumens	CCT	L	H	D
APB3940L30ENES-LW	APB3940L30ENWG-LW	56W	1350 up/2700 down	3000K	38"	4-3/8"	4"
APB5154L30ENES-LW	APB5154L30ENWG-LW	68W	1800 up/3600 down	3000K	50"	4-3/8"	4"



Companions





OVERBED




SCOTT

- Wraparound metal frame
- White acrylic diffuser
- 4-way pull switch with night light

LED

- 120V operation
- 50,000 hr. LED life, 90 CRI

Distressed Grey	LED	Source Lumens	CCT	L	H	D
SCTB3840L30ENDG	56W	1350 up/2700 down	3000K	38"	5"	4"
SCTB5054L30ENDG	68W	1800 up/3600 down	3000K	50"	5"	4"





MARQUETTE

- Walnut finish
- Linen acrylic front diffuser
- White acrylic bottom and top diffuser
- 4-way pull switch with night light

LED

- 120V operation
- 50,000 hr. LED life, 90 CRI

Walnut	LED	Source Lumens	CCT	L	H	D
MQTB3840L30ENWN	56W	1350 up/2700 down	3000K	38"	5"	4"
MQTB5054L30ENWN	68W	1800 up/3600 down	3000K	50"	5"	4"



OVERBED



Espresso/Jute

HARVARD

- Solid wood accent detail
- LumaFuse™ laminated fabric/acrylic shade
- White acrylic bottom and top diffuser
- 4-way pull switch with night light



Weathered Grey/Linen White

LED

- 120V operation
- 50,000 hr. LED life, 90 CRI

Weathered Grey/Jute		Espresso/Jute		LED	Source Lumens	CCT	L	H	D
HVB384000L30ENWG-JT		HVB384000L30ENES-JT		56W	1350 up/2700 down	3000K	38"	4-7/8"	4"
HVB505400L30ENWG-JT		HVB505400L30ENES-JT		68W	1800 up/3600 down	3000K	50"	4-7/8"	4"

Weathered Grey/ Linen White		Espresso/ Linen White		LED	Source Lumens	CCT	L	H	D
HVB384000L30ENWG-LW		HVB384000L30ENES-LW		56W	1350 up/2700 down	3000K	38"	4-7/8"	4"
HVB505400L30ENWG-LW		HVB505400L30ENES-LW		68W	1800 up/3600 down	3000K	50"	4-7/8"	4"





Oil-Rubbed Bronze/Jute

RANDOLPH

- Faux metal finish
- LumaFuse™ laminated fabric/acrylic shade
- White acrylic bottom and top diffuser
- 4-way pull switch with night light

LED

- 120V operation
- 50,000 hr. LED life, 90 CRI



Satin Nickel/Linen White

Satin Nickel/Jute

RAB384000L30ENSN-JT
RAB505400L30ENSN-JT

Oil-Rubbed Bronze/Jute

RAB384000L30ENRB-JT
RAB505400L30ENRB-JT

LED	Source Lumens	CCT	L	H	D
56W	1350 up/2700 down	3000K	38"	4-7/8"	4"
68W	1800 up/3600 down	3000K	50"	4-7/8"	4"


Satin Nickel/Linen White

RAB384000L30ENSN-LW
RAB505400L30ENSN-LW

Oil-Rubbed Bronze/Linen White

RAB384000L30ENRB-LW
RAB505400L30ENRB-LW

LED	Source Lumens	CCT	L	H	D
56W	1350 up/2700 down	3000K	38"	4-7/8"	4"
68W	1800 up/3600 down	3000K	50"	4-7/8"	4"





Weathered Grey/Jute

CLAYTON

- Solid wood accent detail
- LumaFuse™ laminated fabric/acrylic shade
- White acrylic bottom and top diffuser
- 4-way pull switch with night light

LED

- 120V operation
- 50,000 hr. LED life, 90 CRI



Espresso/Linen White

Weathered Grey/Jute		Espresso/Jute		LED	Source Lumens	CCT	L	H	D
CYB384000L30ENWG-JT	CYB384000L30ENES-JT	56W	1350 up/2700 down	3000K	38"	5-1/4"	4"		
CYB505400L30ENWG-JT	CYB505400L30ENES-JT	68W	1800 up/3600 down	3000K	50"	5-1/4"	4"		

Weathered Grey/Linen White		Espresso/Linen White		LED	Source Lumens	CCT	L	H	D
CYB384000L30ENWG-LW	CYB384000L30ENES-LW	56W	1350 up/2700 down	3000K	38"	5-1/4"	4"		
CYB505400L30ENWG-LW	CYB505400L30ENES-LW	68W	1800 up/3600 down	3000K	50"	5-1/4"	4"		





Oil-Rubbed Bronze/Linen White

SHEFFIELD

- Faux metal finish
- LumaFuse™ laminated fabric/acrylic shade
- White acrylic bottom and top diffuser
- 4-way pull switch with night light

LED

- 120V operation
- 50,000 hr. LED life, 90 CRI



Satin Nickel/Linen White

Satin Nickel/Jute

SLB384000L30ENSN-JT
SLB505400L30ENSN-JT

Oil-Rubbed Bronze/Jute

SLB384000L30ENRB-JT
SLB505400L30ENRB-JT

LED	Source Lumens	CCT	L	H	D
56W	1350 up/2700 down	3000K	38"	4-3/8"	4"
68W	1800 up/3600 down	3000K	50"	4-3/8"	4"


Satin Nickel/Linen White

SLB384000L30ENSN-LW
SLB505400L30ENSN-LW

Oil-Rubbed Bronze/Linen White

SLB384000L30ENRB-LW
SLB505400L30ENRB-LW

LED	Source Lumens	CCT	L	H	D
56W	1350 up/2700 down	3000K	38"	4-3/8"	4"
68W	1800 up/3600 down	3000K	50"	4-3/8"	4"



OVERBED



Oakley Bronze

ALGIERS

- Metal trim ends
- Linen acrylic diffuser
- 4-way pull switch with night light

LED

- 120V operation
- 50,000 hr. LED life, 90 CRI



Satin Nickel

Satin Nickel	Oakley Bronze	LED	Source Lumens	CCT	L	H	D
*ALB374000L30ENSN-LA	*ALB374000L30ENKB-LA	56W	1350 up/2700 down	3000K	37-1/4"	5"	4"
ALB495400L30ENSN-LA	ALB495400L30ENKB-LA	68W	1800 up/3600 down	3000K	49-1/4"	5"	4-7/8"



Companions





Satin Nickel

SHERIDAN

- Decorative metal trim
- White linen patterned acrylic front diffuser
- White acrylic bottom and clear top diffuser
- 4-way pull switch with night light



Champagne

LED

- 120V operation
- 50,000 hr. LED life, 90 CRI

Satin Nickel	Champagne	LED	Source Lumens	CCT	L	H	D
SHB444000L30ENSN	SHB444000L30ENAC	56W	1350 up/2700 down	3000K	44-1/4"	4-5/8"	6-1/2"
SHB565400L30ENSN	SHB565400L30ENAC	68W	1800 up/3600 down	3000K	56-1/4"	4-5/8"	6-1/2"

LED

FLUORESCENT

- 120V electronic ballast
- 120-277V universal-voltage option available without switch and nightlight (consult factory)
- Lamps not included

Satin Nickel	Champagne	Qty.	Lamp	L	H	D
SHB325SNE8-LA	SHB325ACE8-LA	3	F25T8	44-1/4"	4-5/8"	6-1/2"
SHB332SNE8-LA	SHB332ACE8-LA	3	F32T8	56-1/4"	4-5/8"	6-1/2"





Overbed Lighting Functions



All On



Downlight



Uplight



Mahogany

IDEAL

- Tapered front with faux wood finish accents
- White acrylic diffuser
- 4-way pull switch with night light

LED

- 120V operation
- 50,000 hr. LED life, 90 CRI



Light Oak

Brushed Nickel	Light Oak	Mahogany	LED	Source Lumens	CCT	L	H	D
IDB394000L30ENBN	IDB394000L30ENLK	IDB394000L30ENMH	56W	1350 up/2700 down	3000K	39-15/16"	5-3/8"	6-1/4"
IDB515400L30ENBN	IDB515400L30ENLK	IDB515400L30ENMH	68W	1800 up/3600 down	3000K	51-15/16"	5-3/8"	6-1/4"



FLUORESCENT

- 120V electronic ballast
- 120-277V universal-voltage option available without switch and night light (consult factory)
- Lamps not included

Brushed Nickel	Light Oak	Mahogany	Qty.	Lamp	L	H	D
IDB325E8BN	IDB325E8LK	IDB325E8MH	3	F25T8	39-15/16"	5-3/8"	6-1/4"
IDB332E8BN	IDB332E8LK	IDB332E8MH	3	F32T8	51-15/16"	5-3/8"	6-1/4"



Companions





Taupe

HINSDALE

- Solid wood crown molding frame
- White acrylic bottom and clear top diffuser
- 4-way pull switch with night light

LED

- 120V operation
- 50,000 hr. LED life, 90 CRI



White

Ivory

Ivory	Taupe	White	LED	Source Lumens	CCT	L	H	D
HDB434000L30ENPI	HDB434000L30ENTT	HDB434000L30ENWH	56W	1350 up/2700 down	3000K	43"	6"	7-1/4"
HDB555400L30ENPI	HDB555400L30ENTT	HDB555400L30ENWH	68W	1800 up/3600 down	3000K	55"	6"	7-1/4"



FLUORESCENT

- 120V electronic ballast
- 120-277V universal-voltage option available without switch and night light (consult factory)
- Lamps not included

Ivory	Taupe	White	Qty.	Lamp	L	H	D
HDB325PIE8	HDB325TTE8	HDB325WHE8	3	F25T8	43"	6"	7-1/4"
HDB332PIE8	HDB332TTE8	HDB332WHE8	3	F32T8	55"	6"	7-1/4"





Espresso

CAMERON

- Solid wood trim frame
- White acrylic bottom and clear top diffuser
- 4-way pull switch with night light

LED

- 120V operation
- 50,000 hr. LED life, 90 CRI



Cherry

Cherry	Espresso	LED	Source Lumens	CCT	L	H	D
CMB394000L30ENCH	CMB394000L30ENES	56W	1350 up/2700 down	3000K	39-5/8"	6"	5-3/4"
CMB515400L30ENCH	CMB515400L30ENES	68W	1800 up/3600 down	3000K	51-5/8"	6"	5-3/4"

LED

FLUORESCENT

- 120V electronic ballast
- 120-277V universal-voltage option available without switch and night light (consult factory)
- Lamps not included

Cherry	Espresso	Qty.	Lamp	L	H	D
CMB325CHE8	CMB325ESE8	3	F25T8	39-5/8"	6"	5-3/4"
CMB332CHE8	CMB332ESE8	3	F32T8	51-5/8"	6"	5-3/4"

FL





PALMETTO

- Off white alabaster acrylic diffuser
- White acrylic bottom and top diffuser
- 4-way pull switch with night light

LED

- 120V operation
- 50,000 hr. LED life, 90 CRI

Alabaster	LED	Source Lumens	CCT	L	H	D
PLB424000L30EN	56W	1350 up/2700 down	3000K	42-1/2"	5-1/4"	5-1/8"
PLB545400L30EN	68W	1800 up/3600 down	3000K	54-1/4"	5-1/4"	5-1/8"



FLUORESCENT

- 120V electronic ballast
- 120-277V universal-voltage option available without switch and night light (consult factory)
- Lamps not included

Alabaster	Qty.	Lamp	L	H	D
PLB325ALE8	3	F25T8	42-1/4"	5-1/4"	5-1/8"
PLB332ALE8	3	F32T8	54-1/4"	5-1/4"	5-1/8"



LINEAR



White

ZURICH

- LED flat panel, low profile construction
- Extruded metal frame


LED

- 120V TRIAC dimmable
- 50,000 hr. LED life, 90 CRI



Satin Nickel
1 ft. x 2 ft.

Satin Nickel		White	LED	Source Lumens	CCT	L	W	H
ZUF12241800L30D1SN	ZUF12241800L30D1WH	ZUF12241800L30D1WH	26W	1800	3000K	27"	15"	2-3/8"
ZUL12483200L30D1SN	ZUL12483200L30D1WH	ZUL12483200L30D1WH	39W	3200	3000K	51"	15"	2-3/8"






White

SLOANE

- LED flat panel, low profile construction
- Extruded metal frame


LED

- 120V TRIAC dimmable
- 50,000 hr. LED life, 90 CRI



Satin Nickel

		Source			L	W	H
		LED	Lumens	CCT			
Satin Nickel	White						
SLF12241800L30D1SN	SLF12241800L30D1WH	26W	1800	3000K	27"	15"	2"
SLL12483200L30D1SN	SLL12483200L30D1WH	39W	3200	3000K	50-1/4"	15"	2"



Companion





Satin Nickel

ATLAS

- LED flat panel, low profile construction
- Extruded metal frame


LED

- 120V TRIAC dimmable
- 50,000 hr. LED life, 90 CRI



Oil-Rubbed Bronze

Satin Nickel		Oil-Rubbed Bronze		LED	Source Lumens	CCT	L	W	H
ATLF12241800L30D1SN	ATLF12241800L30D1RB	26W	1800	3000K	26-3/4"	15"	2"		
ATL12483200L30D1SN	ATL12483200L30D1RB	39W	3200	3000K	50-3/8"	15"	2"		



Companion





Satin Aluminum



Oil-Rubbed Bronze

AEON

- Satin aluminum with white acrylic diffuser
- Oil-rubbed bronze with linen acrylic diffuser

LED

- 50,000 hr. LED life, available in 3000 lumens (28W) or 5000 lumens (46W), 90 CRI

53-3/8" L x **16" W** x 4-3/8" H
 53-3/8" L x **22" W** x 4-3/8" H

Series	Size (Inches)		Source Lumens	LED	CCT	Driver	Finish
	W	L					
AELF	16	=	3000	L	27 2700K	D1 Voltage (120V TRIAC Dimming) D2 Voltage (120-277V 0-10V Dimming)	RB Oil-Rubbed Bronze
	22	=	5000		30 3000K		SA Satin Aluminum

Example: AELF163000L30D1SA





WINCHESTER

- Solid wood crown molding
- Drop dish white acrylic diffuser

LED

- 120V operation
- 50,000 hr. LED life, 90 CRI

White	LED	Source Lumens	CCT	L	W	D
WCM3400L40	33W	3400	4000K	48-3/8"	13"	3-5/8"

LED



NIMBUS

- Narrow profile
- White acrylic diffuser

LED

- 120V operation
- 50,000 hr. LED life, 90 CRI

White	LED	Source Lumens	CCT	L	W	H
NMBL104843L40EN	35W	4300	4000K	48"	12-5/6"	5-1/2"

LED





LED CLOUD

- Narrow profile
- White acrylic diffuser

LED

- 120V TRIAC dimmable
- 50,000 hr. LED life, 90 CRI

Warm White	LED	Source Lumens	CCT	L	W	H
LCL3000L30D1	36W	3000	3000K	49-3/4"	9-3/8"	3-1/4"
LCL4100L30D1	52W	4100	3000K	49-3/4"	9-3/8"	3-1/4"
LCL5000L30D1	60W	5000	3000K	49-3/4"	9-3/8"	3-1/4"

Cool White	LED	Source Lumens	CCT	L	W	H
LCL3000L40D1	36W	3000	4000K	49-3/4"	9-3/8"	3-1/4"
LCL4100L40D1	52W	4100	4000K	49-3/4"	9-3/8"	3-1/4"
LCL5000L40D1	60W	5000	4000K	49-3/4"	9-3/8"	3-1/4"



RIGBY

- Narrow profile
- White acrylic diffuser
- Lift and shift mount

FLUORESCENT

- 120V electronic ballast (R8)
- 120-277V universal-voltage ballast (MV)
- Lamps not included

White	120V	120-277V	Qty.	Lamp	L	W	H
	RC232R8	RC232MV	2	F32T8	50-3/4"	10-1/2"	4-7/8"
	RC2U3R8	RC2U3MV	2	FB32T8	27-1/2"	27"	6"
	RC417R8	RC417MV	4	F17T8	24-1/2"	15"	5-1/4"
	RC432R8	RC432MV	4	F32T8	50-3/4"	15"	5-1/4"



LINEAR



SHAW

- White steel housing
- Frosted acrylic diffuser
- End-to-end connector (included)
- 12" connecting cord (included)

LED

- 120-277V universal-voltage driver
- 50,000 hr. LED life, 80 CRI



White	LED	Source Lumens	CCT	L	W	D
SHAL052220L40MV	25W	2000	4000K	21-1/4"	5-1/4"	2-3/8"
SHAL054840L40MV	40W	4000	4000K	47-1/4"	5-1/4"	2-3/8"



SPRING

- White steel housing
- Clear prismatic diffuser
- Spring loaded end cap for easy lens maintenance

LED

- 120-277V universal voltage driver
- 50,000 hr. LED life, 80 CRI



White	LED	Source Lumens	CCT	L	W	D
SPRL052424L40MV	26W	2500	4000K	24"	5-3/8"	2-3/8"
SPRL054836L40MV	40W	4600	4000K	48"	5-3/8"	2-3/8"





PIERCE

- White steel housing
- White acrylic diffuser

LED

- 120-277V universal-voltage driver
- Compatible with residential (TRIAC/ELV) and commercial (1-10V) dimmers
- 50,000 hr. LED life, 80 CRI
- Adjustable CCT



White	LED	Source Lumens	Adjustable CCT	L	W	D
PRCL450750LAJUDWH	45W	5000	3000K/3500K/4000K	44-7/8"	6-1/2"	2-3/4"



WARSAW

- White steel housing
- Frosted white prismatic acrylic diffuser
- Brushed nickel end caps

LED

- 120-277V universal-voltage driver
- 50,000 hr. LED life, 80 CRI

Brushed Nickel	LED	Source Lumens	CCT	L	W	H
LWL05483600L40SN	39W	3600	4000K	48"	5-1/4"	2-1/2"





LOTUS

- White steel housing
- Frosted white prismatic acrylic diffuser
- White end caps

LED

- 120-277V universal-voltage driver
- 50,000 hr. LED life, 80 CRI

White	LED	Source Lumens	CCT	L	W	H
LWLO7484000L40WH	34W	3800	4000K	48-3/4"	7-9/16"	2-3/4"



FLUORESCENT WRAP

- White steel housing
- Clear prismatic or white acrylic diffuser
- Flush, stem or row mounting

FLUORESCENT

- 120V electronic ballast
- 120-277V universal-voltage ballast
- Lamps not included

Prismatic		Qty.	Lamp	L	W	H
120V	120-277V					
LW217R8	LW217AMV	2	F17T8	24"	7"	2-3/8"
LW232R8	LW232AMV	2	F32T8	48"	7"	2-3/8"
LW432R8	LW432AMV	4	F32T8	48"	11-1/2"	2-3/8"

White		Qty.	Lamp	L	W	H
120V	120-277V					
LW217WAR8	LW217WAMV	2	F17T8	24"	7"	2-3/8"
LW232WAR8	LW232WAMV	2	F32T8	48"	7"	2-3/8"
LW432WAR8	LW432WAMV	4	F32T8	48"	11-1/2"	2-3/8"





LINEAR



LED WRAP

- White steel housing
- Frosted white prismatic acrylic diffuser

LED

- 120V TRIAC dimmable (D1)
- 120-277V universal-voltage driver (MV)
- 120-277V, 0-10V DC dimmable (D2)
- 50,000 hr. LED life, 90 CRI

Warm White	LED	Source Lumens	CCT	L	W	H
*LWL07242500L30D1	30W	2500	3000K	24"	7"	2-3/8"
*LWL07483000L30D1	36W	3000	3000K	48"	7"	2-3/8"
*LWL07485000L30D1	60W	5000	3000K	48"	7"	2-3/8"
*LWL07242500L30D2	30W	2500	3000K	24"	7"	2-3/8"
*LWL07483000L30D2	36W	3000	3000K	48"	7"	2-3/8"
*LWL07485000L30D2	60W	5000	3000K	48"	7"	2-3/8"

Cool White	LED	Source Lumens	CCT	L	W	H
*LWL07242500L40D1	30W	2500	4000K	24"	7"	2-3/8"
*LWL07483000L40D1	36W	3000	4000K	48"	7"	2-3/8"
LWL07483600L40MV	30W	3600	4000K	48"	7"	2-1/2"
*LWL07485000L40D1	60W	5000	4000K	48"	7"	2-3/8"
*LWL07242500L40D2	30W	2500	4000K	24"	7"	2-3/8"
*LWL07483000L40D2	36W	3000	4000K	48"	7"	2-3/8"
*LWL07485000L40D2	60W	5000	4000K	48"	7"	2-3/8"
LWL13487200L40MV	52W	6200	4000K	48"	11-1/2"	2-1/2"



LED WRAP CHASSIS

- White steel housing
- Frosted white prismatic acrylic diffuser

CHASSIS WITHOUT BALLAST

- For use with Type B, ballast bypass, LED tubes
- Single ended or double ended
- Lamp(s) not included

Prismatic	Lamp Qty.	L	W	H	White	Lamp Qty.	L	W	H
LWL0724SP	2	24"	7"	2-3/8"	LWL0724SW	2	24"	7"	2-3/8"
LWL0748SP	2	48"	7"	2-3/8"	LWL0748SW	2	48"	7"	2-3/8"
LWL1148SP	4	48"	11-1/2"	2-3/8"	LWL1148SW	4	48"	11-1/2"	2-3/8"





CORONADO LED STRIPLIGHT

- Pre-finished white steel housing
- White acrylic diffuser

LED

- 120-277V universal-voltage driver
- 50,000 hr. LED life, 80 CRI

Cool White	LED	Source Lumens	CCT	L	W	H
CRDLO22419L40MVWH	17W	1900	4000K	24"	2-1/2"	2-1/2"
CRDLO24624L40MVWH	22W	2400	4000K	46-1/2"	2-1/2"	2-1/2"
CRDLO24647L40MVWH	43W	4700	4000K	46-1/2"	2-1/2"	2-1/2"



LISLE LED STRIPLIGHT

- Pre-finished white steel housing
- White acrylic diffuser

LED

- 120-277V universal-voltage driver
- 50,000 hr. LED life, 90 CRI

Cool White	LED	Source Lumens	CCT	L	W	H
LSL484100L40MVWH	34W	4100	4000K	48"	5"	3-5/16"





STANDARD STRIPLIGHT

- Pre-finished white steel housing
- Flush, stem or row mounting

FLUORESCENT

- 120V electronic ballast
- 120-277V universal-voltage ballast
- Lamp(s) not included

Single

120V	120-277V	Qty.	Lamp	L	W	H
ST115R8		1	F15T8	18"	3-1/8"	3-1/4"
ST117R8	ST117MV	1	F17T8	24"	3-1/8"	3-1/4"
ST125R8	ST125MV	1	F25T8	36"	3-1/8"	3-1/4"
ST132R8	ST132MV	1	F32T8	48"	3-1/8"	3-1/4"

Double

120V	120-277V	Qty.	Lamp	L	W	H
ST217R8	ST217MV	2	F17T8	24"	4-3/4"	3-3/4"
ST225R8	ST225MV	2	F25T8	36"	4-3/4"	3-3/4"
ST232R8	ST232MV	2	F32T8	48"	4-3/4"	3-3/4"
	ST232-8MV	4	F32T8	96"	4-3/4"	3-3/4"



CHASSIS WITHOUT BALLAST

- For use with Type B, ballast bypass, LED tubes
- Single ended or double ended
- Lamp(s) not included

Single	Lamp Qty.	Suitable Base Type	L	W	H
ST1L18	1	G13-Medium Base	18"	2-5/8"	3-1/4"
ST1L24	1	G13-Medium Base	24"	3-1/8"	3-1/4"
ST1L36	1	G13-Medium Base	36"	3-1/8"	3-1/4"
ST1L48	1	G13-Medium Base	48"	3-1/8"	3-1/4"

Double	Lamp Qty.	Suitable Base Type	L	W	H
ST2L24	2	G13-Medium Base	24"	4-3/4"	3-3/4"
ST2L36	2	G13-Medium Base	36"	4-3/4"	3-3/4"
ST2L48	2	G13-Medium Base	48"	4-3/4"	3-3/4"
ST4L96	4	G13-Medium Base	96"	4-3/4"	3-3/4" (Tandem)
ST2L96-FA8	2	FA8-Single Pin No Lamp	96"	4-3/4"	3-3/4"
ST2L96-R17D	2	R17D-Recessed Double Contact	96"	4-3/4"	3-3/4"



Single



Double



COMMERCIAL GRADE STRIPLIGHT

- Pre-finished white steel housing
- Flush, stem or row mounting

FLUORESCENT

- 120-277V universal-voltage ballast
- Lamps not included

430 mA Slimline

120-277V	Qty.	Lamp	L	W	H
S296MV	2	F96T8	96"	4-1/4"	3-3/4"



LOW-PROFILE STRIPLIGHT

- Pre-finished white steel housing
- Flush, stem or row mounting

FLUORESCENT

- 120-277V universal-voltage ballast
- Energy efficient T5 technology
- Lamp(s) not included

Single	Qty.	Lamp	L	W	H
STN114MV	1	F14T5	22-3/8"	1-7/8"	2-3/8"
STN121MV	1	F21T5	34-3/8"	1-7/8"	2-3/8"
STN128MV	1	F28T5	46-3/8"	1-7/8"	2-3/8"

Double	Qty.	Lamp	L	W	H
STN214MV	2	F14T5	22-3/4"	3-1/8"	2-3/8"
STN221MV	2	F21T5	34-3/4"	3-1/8"	2-3/8"
STN228MV	2	F28T5	46-3/4"	3-1/8"	2-3/8"



Single



Double



LED VAPORTITE

- Impact resistant white polycarbonate housing
- Clear polycarbonate diffuser
- Continuous gasket offers secure seal against dust and moisture
- Includes mounting brackets and water tight connector

LED

- 120-277V universal-voltage driver
- 50,000 hr. LED life, 90 CRI

Cool White	LED	Source Lumens	CCT	L	W	H
VTL483500L40MV	34W	3500	4000K	48"	6-3/4"	5-1/8"



VAPORTITE

- Reinforced fiberglass housing
- Spring mounted easy install diffuser brackets
- Molded, high impact acrylic
- Continuous gasket offers secure seal against dust and moisture
- Includes mounting brackets and water tight connector

FLUORESCENT

- 120-277V universal-voltage ballast
- Lamps not included

White	Qty.	Lamp	L	W	H
VTL228MV	2	F28T5	50"	6-3/4"	5-1/8"
VTL232MV	2	F32T8	50"	6-3/4"	5-1/8"
VTL228-8MV	4	F28T5	98"	6-3/4"	5-1/8"
VTL232-8MV	4	F32T8	98"	6-3/4"	5-1/8"



UNDERCABINET

SLATE™ PRO 2.0

TAKE CONTROL



App



WiFi



Bluetooth



Remote



Voice



Brightness and Color, both at your command

For new construction or renovation, the Slate Pro Color-Control LED System provides unprecedented flexibility to tailor under-cabinet lighting to suit the setting, facilitate a task, or set the mood. Evenly lit, glare-free illumination featuring the latest in low-profile LED technology is driven by an innovative 3-function control that brings dimming and color temperature within your reach.



VOICE

CCT 2700K-4000K
90+ CRI
Full-range dimming
Glare-free



REMOTE



APP

Voice controlled
Energy Star® and T24
Programmable
Low profile

Slate's dual adjustment has been designed to give control over lighting the kitchen environment. While preparing food for dinner guests, a full brightness may be preferred, with color temperature set to a cool and clean visibility level. When company arrives, a more sociable mood can be created by bringing the dimmer down and adjusting to a warm setting.



FULL-RANGE
WARM-TO-COOL



FULL-RANGE
DIMMING CONTROL



4000°K
Cool Daylight



2700°K
Warm White

UNDERCABINET



FLEXIBLE POWER SUPPLY INSTALLATION

Versatile in-wall or under cabinet installation with wireless remote


The Slate Pro control can be easily installed in-wall, or surface-mounted for full installation flexibility. The versatile power supply can be hard-wired or plugged into any standard 110v outlet.

WIRELESS BLUETOOTH CONTROLLER

Easy to specify, Easy to install

- The SPLE Starter Kit can accommodate up to 72 watts of LED panels.
- Secondary power supplies can be added to expand system up to 144W total.
- Multiple systems can be linked together to work with a single controller.

panel size	panel watts	qty	total watts
14"	7	2	14.0
22"	11	3	33.0
40"	20.5	1	20.5
total			67.5 watts



SLATE™ PRO 2.0

Wireless Color-Control LED Panel System

- One-touch full-range dimming
- One-touch color temperature (CCT) adjustment, from warm to cool (2700°K-4000°K)
- Edge-Lit LED panels provide evenly distributed, glare-free light for all surfaces
- Linkable panels includes multiple connectors for a variety of layout options
- Ultra-low 1/2" LED panel profile
- Dual-run capability allows full installation flexibility
- 500 lumens per foot, 90 CRI
- Powder-coated housing with molded end caps
- Each panel includes 12" connecting cable and direct connector
- Easy, flexible DC installation
- 120VAC input, 36W - 144W DC (Depending on Power Supply)
- 2 power supply options (36W and 72W)
- Optional occupancy sensor (motion), page 292
- Patent Pending



LED Panels


Size	White	Oil-Rubbed Bronze	Lumens Watts	4000K	LPW	L W D		
						L	W	D
9 in.	SPLE9WH	SPLE9RB	4.5W	375	58	9"	5"	1/2"
14 in.	SPLE14WH	SPLE14RB	7.5W	585	60	14"	5"	1/2"
22 in.	SPLE22WH	SPLE22RB	12W	920	60	22"	5"	1/2"
32 in.	SPLE32WH	SPLE32RB	18W	1330	60	32"	5"	1/2"
40 in.	SPLE40WH	SPLE40RB	22W	1670	60	40"	5"	1/2"

Each panel includes (1) one:
 - 12" interconnect cord
 - Direct connector

STARTER KIT


SPLE-STARTER

- (1) RF Controller
- (1) 72W RF Power Supply Unit
- (1) 10' DC Input Cord
- (1) 5' AC Power Cord
- (1) Wall Cover Plate
- (1) Optional J-Box Mounting Bracket



ACCESSORY

- SPLECL24 | 24" Interconnect cord
- SPLECL36 | 36" Interconnect cord
- SPLECL48 | 48" Interconnect cord
- SPLECL72 | 72" Interconnect cord
- SPLEDC | Direct Connector
- LCX-PWR36 | 36W Power Supply
- LCX-PWR72 | 72W Power Supply



How to order

SPLE-STARTER + PANELS + ACCESSORY (as needed)






KOREN

- Low profile
- Extruded aluminum housing
- Linkable up to 200W with connecting cable or direct connector
- Selectable switch: choose 1 of 3 colors of 2700K, 3000K or 4000K
- Hi/low switch
- Rear access plate for quick wire connections
- Captive mounting screws
- Plug-in or direct wire
- Extruded aluminum construction
- 100,000 hr. LED life, 90 CRI
- Additional accessories and optional occupancy sensor (motion), page 292
- Patent pending

Size	White	Oil-Rubbed Bronze	Type	Lumens			LPW	L	W	D
				2.7K	3.0K	4.0K				
9 in.	KNLU9WH	KNLU9RB	4.8W SMT-Array	253	265	281	55	9"	3"	5/8"
14 in.	KNLU14WH	KNLU14RB	7.4W SMT-Array	405	446	484	60	14"	3"	5/8"
22 in.	KNLU22WH	KNLU22RB	11.8W SMT-Array	629	682	715	58	22"	3"	5/8"
32 in.	KNLU32WH	KNLU32RB	15.3W SMT-Array	905	955	980	62	32"	3"	5/8"
40 in.	KNLU40WH	KNLU40RB	19.5W SMT-Array	1069	1150	1182	59	40"	3"	5/8"

LPW based on 3000K color temperature



Accessories



Order separately, see page 292



UNDERCABINET




LED NOBLE PRO

- Plug-in or direct wire
- Linkable up to 200 watts with 12" connecting cable or direct wire
- Selectable switch: choose 1 of 3 colors of 2700K, 3000K or 4000K
- White polycarbonate diffuser hides LEDs
- Fully integrated LEDs
- ≥ 90 CRI
- 50,000 hour LED life
- Hi-Low switch
- Rear access plate for quick wire connections
- Captive mounting screws
- Includes: connecting cable, cord & plug, direct connector & hardwire connector
- Extruded aluminum construction
- Additional accessories and optional occupancy sensor (motion), page 292

Size	White	Oil-Rubbed Bronze	Brushed Aluminum	Type	Lumens			LPW	L	W	D
					2.7K	3.0K	4.0K				
9 in.	NLLP9WH	NLLP9RB	NLLP9BA	4.6W SMT-Array	259	290	384	63	9"	3-3/4"	1"
14 in.	NLLP14WH	NLLP14RB	NLLP14BA	6.7W SMT-Array	384	437	442	65	14"	3-3/4"	1"
22 in.	NLLP22WH	NLLP22RB	NLLP22BA	10.7W SMT-Array	656	746	755	69	22"	3-3/4"	1"
32 in.	NLLP32WH	NLLP32RB	NLLP32BA	14.4W SMT-Array	927	1022	1023	70	32"	3-3/4"	1"
40 in.	NLLP40WH	NLLP40RB	NLLP40BA	18W SMT-Array	1170	1302	1310	72	40"	3-3/4"	1"

LPW based on 3000K color temperature



Accessories



Order separately, see page 292



UNDERCABINET

LED T5L



- Direct wire
- Hardwire only
- 3000K color temperature
- White polycarbonate diffuser hides LEDs
- Fully integrated LEDs
- ≥ 90 CRI
- 50,000 hour LED life
- On/off switch
- Multiple knockouts conveniently located
- Includes hardwire connector
- Stamped steel construction
- Optional occupancy sensor (motion), page 292

Size	White	Oil-Rubbed Bronze	Type	Lumens	LPW	L	W	D
9 in.	T5L9RWH	_____	5W SMT-Array	220	44	9"	3-1/2"	1-1/8"
12 in.	T5L12RWH	T5L12RRB	5W SMT-Array	315	63	12"	3-1/2"	1-1/8"
18 in.	T5L18RWH	T5L18RRB	7.5W SMT-Array	520	69	18"	3-1/2"	1-1/8"
21 in.	T5L21RWH	T5L21RRB	8.5W SMT-Array	570	67	21"	3-1/2"	1-1/8"
24 in.	T5L24RWH	T5L24RRB	9W SMT-Array	630	70	24"	3-1/2"	1-1/8"
33 in.	T5L33RWH	T5L33RRB	13.5W SMT-Array	950	70	33"	3-1/2"	1-1/8"
42 in.	T5L42RWH	T5L42RRB	16.5W SMT-Array	1150	69	42"	3-1/2"	1-1/8"



Accessories





T5LCLTP

T5L CLOSET

- White steel housing
- White acrylic diffuser
- Standard knockouts

LED

- 120V operation
- 50,000 hr. LED life, 90 CRI



T5LCLT

White	LED	Source Lumens	CCT	L	W	D
T5LCLT (on/off rocker switch)	9W	700	4000K	18"	4-1/2"	1-3/8"
T5LCLTP (on/off pull chain switch)	9W	700	4000K	18"	4-1/2"	1-3/8"



UNDERCABINET

Additional Accessories Noble Pro/NXL Series

White Model #s

XLCP60WH

- 60" Cord & Plug

XLHBWH

- Hardwire Box

XLCC24WH

- 24" Interconnect Cord

XLCC36WH

- 36" Interconnect Cord

XLCC48WH

- 48" Interconnect Cord

XLCC72WH

- 72" Interconnect Cord

Black Model #s

XLCP60BL

- 60" Cord & Plug

XLHBBL

- Hardwire Box

XLCC24BL

- 24" Interconnect Cord

XLCC36BL

- 36" Interconnect Cord

XLCC48BL

- 48" Interconnect Cord

XLCC72BL

- 72" Interconnect Cord

Model # XLC-Clip

- Clear cord clip with screws
(4 pieces)

Occupancy Sensor (Motion) for Slate Pro 2.0/Nobel Pro/T5L

Model # LCX-OCC

- Microwave sensor unit, on/off rocker switch
- Includes connecting cables that operate with Noble Pro (NLLP), xenon (NXL)
- Hardwire for T5L and Slate Pro (SPLE)





Hera[®]

Light Years Ahead.

AFX Partner

Hera designs, develops and manufactures high-quality lighting solutions specifically for cabinets, furniture and displays. Hera comes from a European heritage in innovative lighting design and technology and as manufacturers develop our own unique lighting systems.

Hera's expertise in bringing new trends and technology to the market has been evident throughout the decades. As a driving force in lighting technology, Hera's main focus for more than a decade has been LED technology -- bringing energy-efficient and maintenance free LEDs to market.

All Hera lighting products are unique, stylishly designed and on the leading edge of today's lighting technology, with lighting systems that exemplify beauty as well as form and function.





STICK 2 LED

MINI LINEAR LED WITH INTEGRATED CONNECTING SYSTEM

- Aluminum and plexiglass housing
- Recess or surface mount
- 50,000 hr. life
- Dimmable with optional accessories (consult factory)
- Uses: furniture, cabinets, displays, closets, food cases

3000K	Watt	Lumens	L	W	D
STICK2/8/WW	1.6	80	8"	7/16"	3/8"
STICK2/12/WW	2.4	109	12"	7/16"	3/8"
STICK2/34/WW	7.2	341	34"	7/16"	3/8"
STICK2/46/WW	9.7	461	46"	7/16"	3/8"

4100K	Watt	Lumens	L	W	D
STICK2/8/CW	1.6	70	8"	7/16"	3/8"
STICK2/12/CW	2.4	107	12"	7/16"	3/8"
STICK2/34/CW	7.2	304	34"	7/16"	3/8"
STICK2/46/CW	9.7	411	46"	7/16"	3/8"

Accessories	
STICK2/PC	Power cord 98"
STICK2/CC1	1" connecting cable
STICK2/CC12	12" connecting cable
STICK2/CC39	39" connecting cable
STICK/TB	Terminal block
KB12LEDCC39	39" power cable
KB12LEDCC98	98" power cable

Drivers	
STICKPS24/6WATT	6 watt
STICKPS24/30HE	30 watt
STICKPS24/75	75 watt
STICKPS24/96/DIM	96 watt



STICK 3 LED

MINI LINEAR LED WITH INTEGRATED CONNECTING SYSTEM

- Aluminum housing
- Frosted light lens
- Recess or surface mount
- 50,000 hr. life
- Dimmable with optional accessories (consult factory)
- Uses: furniture, cabinets, displays, show cases

3000K	Watt	Lumens	L	W	D
STICK3/8/WW	2.5	260	7-7/8"	1/2"	1/2"
STICK3/12/WW	4	420	11-13/16"	1/2"	1/2"
STICK3/24/WW	7.5	840	22-7/16"	1/2"	1/2"
STICK3/34/WW	11.5	1260	34-1/4"	1/2"	1/2"
STICK3/46/WW	15	1680	44-7/8"	1/2"	1/2"

4100K	Watt	Lumens	L	W	D
STICK3/8/CW	2.5	260	7-7/8"	1/2"	1/2"
STICK3/12/CW	4	420	11-13/16"	1/2"	1/2"
STICK3/24/CW	7.5	840	22-7/16"	1/2"	1/2"
STICK3/34/CW	11.5	1260	34-1/4"	1/2"	1/2"
STICK3/46/CW	15	1680	44-7/8"	1/2"	1/2"

Accessories	
STICK3/PC	Power cord 59"
STICK3/CC2	2" connecting cable
STICK3/CC12	12" connecting cable
STICK3/CC39	39" connecting cable
STICK/TB	Terminal block
KB12LEDCC39	39" power cable
KB12LEDCC98	98" power cable

Drivers	
STICKPS24/6WATT	6 watt
STICKPS24/30HE	30 watt
STICKPS24/75	75 watt
STICKPS24/96/DIM	96 watt



ELITE LED

LINEAR LED WITH DIRECT CONNECT SYSTEM

- Aluminum housing with frosted lens
- Recess or surface mount
- 50,000 hr. life
- Uses: furniture, cabinets, displays

3000K	Watt	Lumens	L	W	D
EL/LED/12/WW	5	320	11"	1"	1-3/8"
EL/LED/22/WW	9	700	21-3/16"	1"	1-3/8"
EL/LED/34/WW	12	950	33"	1"	1-3/8"
EL/LED/46/WW	15	1200	44-13/16"	1"	1-3/8"
EL/LED/59/WW	18	1550	56-5/8"	1"	1-3/8"

Accessories

Connecting cables from 6" to 144"
Straight or 90°

Power Cords

With plug from 36" to 144"

4100K	Watt	Lumens	L	W	D
EL/LED/12/CW	5	320	11"	1"	1-3/8"
EL/LED/22/CW	9	700	21-3/16"	1"	1-3/8"
EL/LED/34/CW	12	950	33"	1"	1-3/8"
EL/LED/46/CW	15	1200	44-13/16"	1"	1-3/8"
EL/LED/59/CW	18	1550	56-5/8"	1"	1-3/8"

Consult factory



SLIMLITE XL T5

LINEAR FLUORESCENT WITH DIRECT CONNECT SYSTEM

- Steel housing and aluminum with optional lens (order separately)
- Surface mount
- Energy efficient T5 lamps (order separately)
- Electronic ballast
- Uses: shelves, cabinets, displays, food applications

White	Lamp	Lumens	L	W	H
ES12/R	F8WT5	400	12-7/8"	7/8"	1-5/16"
ES22/R	F14WT5	1350	23-1/8"	7/8"	1-5/16"
ES34/R	F21T5	2100	34-7/8"	7/8"	1-5/16"
ES46/R	F28T5	2900	46-3/4"	7/8"	1-5/16"
ES59/R	F35T5	3650	58-7/16"	7/8"	1-5/16"

Accessories

SCC6/XL/R 6" connecting cable
 SCC12/XL/R 12" connecting cable
 SCC24/XL/R 24" connecting cable
 SCC48/XL/R 48" connecting cable
 SCC72/XL/R 72" connecting cable
 SCC120/XL/R 120" connecting cable
 SDC/XL/R Direct connect

Power Cords

SPC/XL/R 72"
 SPC/S/XL/R 72" with roller switch
 SPC72/STC 72" with straight connector



R55

LED SPOTLIGHT

- Aluminum housing
- Recess or surface mount
- 50,000 hr. life
- Dimmable with optional accessories (consult factory)
- Uses: furniture, cabinets, displays

3000K	Color	Watt	Lumens	Dia	D
R55-LED/SS/WW	Stainless Steel	3	165	2-11/16"	7/16"
R55-LED/CH/WW	Matte Chrome	3	165	2-11/16"	7/16"
R55-LED/BL/WW	Black	3	165	2-11/16"	7/16"
R55-LED/WH/WW	White	3	165	2-11/16"	7/16"

4100K	Color	Watt	Lumens	Dia	D
R55-LED/SS/CW	Stainless Steel	3	165	2-11/16"	7/16"
R55-LED/CH/CW	Matte Chrome	3	165	2-11/16"	7/16"
R55-LED/BL/CW	Black	3	165	2-11/16"	7/16"
R55-LED/WH/CW	White	3	165	2-11/16"	7/16"

Accessories	
STICK/TB	Terminal block
KB12LEDCC39	39" power cable
KB12LEDCC98	98" power cable

Drivers	
STICKPS24/6WATT	6 watt
STICKPS24/30HE	30 watt
STICKPS24/75	75 watt
STICKPS24/96/DIM	96 watt



FR68

LED SPOTLIGHT

- Aluminum housing with frosted lens
- Recess or surface mount
- 50,000 hr. life
- Dimmable with optional accessories (consult factory)
- Uses: furniture, cabinets, displays

3000K	Color	Watt	Lumens	Dia	D
FR68/SS/3000	Stainless Steel	4	230	2-15/16"	9/16"
FR68/MC/3000	Matte Chrome	4	230	2-15/16"	9/16"

4000K	Color	Watt	Lumens	Dia	D
FR68/SS/4000	Stainless Steel	4	230	2-15/16"	9/16"
FR68/MC/4000	Matte Chrome	4	230	2-15/16"	9/16"

Accessories	
STICK/TB	Terminal block
KB12LEDCC39	39" power cable
KB12LEDCC98	98" power cable

Drivers	
STICKPS24/6WATT	6 watt
STICKPS24/30HE	30 watt
STICKPS24/75	75 watt
STICKPS24/96/DIM	96 watt





EYE-LED LED MINI SPOTLIGHT

- Aluminum housing
- Recess mount
- 50,000 hr. life
- Dimmable with optional accessories (consult factory)
- Uses: furniture, cabinets, displays, closets



3000K	Color	Watt	Lumens	Dia	D	Accessories	
EYELEDSS/WW	Stainless Steel	1	60	1-1/8"	1/2"	LEDCC36	36" connecting cable
EYELEDA/WW	Aluminum	1	60	1-1/8"	1/2"	LEDCC72	72" connecting cable
						TBLED/B	Terminal block
4000K	Color	Watt	Lumens	Dia	D	Drivers	
EYELEDSS/CW	Stainless Steel	1	80	1-1/8"	1/2"	PSLED10	10 watt
EYELEDA/CW	Aluminum	1	80	1-1/8"	1/2"	PSLED/DIM/S	18 watt dimmable
						DIMCONTROL	LED dimmer control

SR68

LED SWIVEL SPOTLIGHT

- Aluminum housing with frosted lens
- Recess mount with 20° swivel and tilt
- 50,000 hr. life
- Dimmable with optional accessories (consult factory)
- Uses: furniture, cabinets, displays, closets

3000K	Color	Watt	Lumens	Dia	D
SR68/WW	Brushed Aluminum	4.8	283	3-3/16"	1-9/16"

4000K	Color	Watt	Lumens	Dia	D
SR68/CW	Brushed Aluminum	4.8	283	3-3/16"	1-9/16"

Accessories	
LEDCC36	36" connecting cable
LEDCC72	72" connecting cable

Drivers	
PSLED/10	10 watt
PSLED/DIM/S	18 watt dimmable
DIMCONTROL	LED dimmer control



SR45

LED SWIVEL SPOTLIGHT

- Aluminum housing
- Recess mount with 20° swivel and tilt
- 50,000 hr. life
- Dimmable with optional accessories (consult factory)
- Uses: furniture, cabinets, displays, closets


3000K	Color	Watt	Lumens	Dia	D
SR45/SS/3000	Stainless Steel	5.3	422	2"	1-1/4"
SR45/WH/3000	White	5.3	422	2"	1-1/4"

4000K	Color	Watt	Lumens	Dia	D
SR45/SS/4000	Stainless Steel	5.3	422	2"	1-1/4"
SR45/WH/4000	White	5.3	422	2"	1-1/4"

Accessories	
LEDCC36	36" connecting cable
LEDCC72	72" connecting cable

Drivers	
PSLED/10	10 watt
PSLED/DIM/S	18 watt dimmable
DIMCONTROL	LED dimmer control





Custom Capabilities

Making your vision a reality.

At AFX, we appreciate that every space and application is unique to each designer's vision. To accommodate flexibility and creativity, AFX product lines are engineered with the idea that they can be customized to satisfy each client's project requirements.

If you don't see the exact solution from among our standard product offerings, AFX gives you the freedom to create your own lighting solution. From stock to modifications to full custom, we offer numerous options to meet your specific needs. To support projects requiring quick turnaround, we also maintain sufficient inventory levels on many items to meet job quantity requirements. For custom fabric and finish options please consult factory.



LED Evolution

LED's (light-emitting diodes) bring several advantages to the lighting industry, including high efficacy and durability. With superior life over other lamp sources (50,000 hours+), the required maintenance for LED products is greatly reduced. This translates into energy savings and environmental sustainability. LEDs create greater optical control (more controllable source), dimming, instant on/off, and reduced rate of lumen depreciation (potential for long application life). The use of LED luminaires in commercial and residential applications is viable today both economically and from an illumination performance standpoint. The advances in LED technology allow AFX to bring these products to the marketplace via retrofitting, hybrid or new designs to meet a variety of lighting applications.

LED Features and Benefits

Long-lasting—LEDs last up to 5 times longer than compact fluorescents, and far longer than typical incandescent lamps. Average LED lamp life: 50,000 hrs.

Cold weather—Excellent for use in cold climates.

Durable—Since LEDs do not have filament, they are not damaged under circumstances when regular incandescent bulb would be broken.

Instant-On—LED fixtures turn on instantly in all weather conditions.

Cool—LEDs produce 3.4 btu's/hour, compared to 85 btu's for incandescent bulbs.

Mercury-free—No mercury is used in the manufacturing of LEDs.

More efficient—LEDs use only 2-10 watts of electricity (1/3rd to 1/30th of incandescent or CFL).

Cost effective—Although LEDs are more expensive than CFL or incandescent, the cost is recouped over time in energy savings, maintenance reduction and little to no replacement costs.



ENERGY STAR®

Through innovation and design, AFX is creating the next generation of energy-efficient fixtures by proving that energy-efficient lighting doesn't have to be uninteresting. As you browse through our catalog look for the ENERGY STAR logo. This identifies ENERGY STAR qualified products throughout this catalog. Consult factory or www.energystar.gov for current listing.




AFX has dedicated to being environmentally responsible and preserving our natural resources. As a company we continually strive to reduce our carbon footprint and global emissions, not only in the products we sell, but in the materials we use to promote them. Our philosophy of offering products that are technologically advanced as well as energy efficient runs through our company down to our internal recycling program.

Fluorescent lamps contain trace amounts of Mercury. If lamp is marked Hg it contains Mercury and must be disposed of properly. Follow local and/or state laws regarding disposal of fluorescent lamps. Information regarding lamp recycling can be found at www.epa.gov/cfl or www.lamprecycle.org

Color Temperature

When selecting bulbs for AFX fixtures, it's important to consider color temperature in relation to the application. Whether for a residence or a commercial space, for a productive environment or leisure area, it's a subjective and personal choice. But, there are some generally accepted standards: Warm light is better for residential living areas; cool light is better for task areas such as the kitchen or office. Current energy-efficient technology allows for a high level of quality across the whole color spectrum, so the choice is yours. The chart below offers some suggestions. Consult your lamp supplier for more specific applications.



Ballast Troubleshooting

It is important to know which ballast is in the fluorescent fixture and which lamp is compatible with that ballast. Not using the correct lamp may result in ballast overheating, ballast thermal cycling or premature ballast failure. AFX products offer superior ballasting, but it is very important to use the proper lamp for optimum performance. Here are several tips for ballast troubleshooting:

SYMPTOM	CORRECTIVE ACTION
LAMPS WILL NOT OPERATE	<ol style="list-style-type: none"> 1. CHECK IF THERE IS POWER TO THE FIXTURE 2. BE SURE LAMP IS PROPERLY SEATED IN SOCKET 3. REPLACE LAMP 4. RESET OR CHANGE STARTER (PREHEAT ONLY) 5. CHECK WIRING CONNECTIONS 6. TEST BALLAST
SLOW OR ERRATIC STARTING	<ol style="list-style-type: none"> 1. CHECK GROUND (FIXTURE MUST BE GROUNDED FOR RELIABLE STARTING) 2. CHECK BALLAST LABEL FOR CORRECT LAMP 3. CHECK WIRING CONNECTIONS 4. CHECK FOR LOW SUPPLY VOLTAGE 5. BE SURE LAMP IS PROPERLY SEATED IN SOCKET 6. TEST BALLAST
EXCESSIVE NOISE	<ol style="list-style-type: none"> 1. TIGHTEN LOOSE COMPONENTS 2. INSTALL BALLASTS OF THE PROPER SOUND RATING 3. REPLACE FAULTY BALLAST(S). NORMAL OPERATION SHOULD RESUME 4. NOTE: ALL FLUORESCENT BALLASTS EMIT SOME NOISE
LAMPS ARE CYCLING	<ol style="list-style-type: none"> 1. CHECK AIR TEMPERATURE IN AND AROUND THE FIXTURE 2. CHECK BALLAST AND COIL TEMPERATURES - BALLAST CASE TEMPERATURES SHOULD NOT EXCEED 90°C AND COIL TEMPERATURES SHOULD NOT EXCEED 105°C 3. REMOVE BUILDING INSULATION FROM ABOVE FIXTURES TO ALLOW FOR HEAT DISSIPATION 4. REPLACE FAULTY BALLAST(S). NORMAL OPERATION SHOULD RESUME
INTERFERENCE	<ol style="list-style-type: none"> 1. RADIO AND ANTENNA MUST BE 4 - 10 FEET FROM LAMPS 2. CORRECT CONDITION BY USE OF RADIO INTERFERENCE FILTERS 3. LIGHTING FIXTURES SHOULD BE ON SEPARATE ELECTRICAL

Linear Electronic Ballast and Lamp System Performance

BALLAST TYPE	LAMP DESCRIPTION	VOLTAGE	LAMP WATTS	LAMP SIZE	DESCRIPTION	LIFE HOURS	APPROX. INPUT WATTS	INITIAL DELIVERED LUMENS	THD%	POWER FACTOR	AMPS
R8	RESIDENTIAL ELECTRONIC NORMAL POWER FACTOR 120V		32W	T8	F32T8/TL841	20,000	56	5016	≤ 120	≥ 50	
MV	COMMERCIAL/RESIDENTIAL ELECTRONIC HIGH POWER FACTOR	120V 277V	32W 32W	T8 T8	F32T8/TL841 F32T8/TL841	20,000 24,000	58 56	5016 5251	≤ 30 ≤ 10	≥ 90 ≥ 99	.49 .22
EN	RESIDENTIAL	120V	32W	CFQ	PL-C-4 PIN	12,000	51	3420	≤ 10	≥ 99	.43

LED Driver System Performance

DRIVER TYPE	DESCRIPTION	INPUT VOLTAGE	OUTPUT CURRENT (mA)	POWER FACTOR	MIN. STARTING TEMP.	DIMMABLE
D1	RESIDENTIAL ELECTRONIC HIGH POWER FACTOR	120V	220-800	>0.90	-30°F/-34°C	YES - TRIAC (FORWARD PHASE OR LEADING-EDGE)/ ELV (REVERSE-PHASE OR TRAILING-EDGE)
MV	COMMERCIAL/RESIDENTIAL ELECTRONIC HIGH POWER FACTOR	120-277V	350-800	>0.90	-30°F/-34°C	NO
UD	COMMERCIAL/RESIDENTIAL ELECTRONIC HIGH POWER FACTOR	120-277V	250-2100	>0.90	-30°F/-34°C	YES - TRIAC (FORWARD PHASE OR LEADING -EDGE)/ ELV (REVERSE-PHASE OR TRAILING-EDGE)
D2	COMMERCIAL ELECTRONIC HIGH POWER FACTOR	120-277V	350-800	>0.90	-30°F/-34°C	AND 0-10V YES - 0-10V

Lighting Definitions

BALLAST FACTOR – Ratio of a lamp’s light output on ballast compared to the lamp’s rated light output. The higher the ballast factor, the more light delivered.

CIRCLE E BALLAST – Indicates special EFACT compliant version of ballast. Check the laws and codes for specific applications.

COLOR TEMPERATURE OR CHROMATICITY – The appearance of the light that comes from a light source. The color temperature is measured in Kelvin or “K”. The higher the color temperature, the visually cooler or bluer the light appears.

COLOR RENDERING INDEX – CRI indicates how true-to-color lighted objects appear. A higher number means truer color. The CRI rates light sources on a scale of 0 to 100. The higher the CRI, the more vibrant or close to natural the colors of objects appear. Light from lamps with good (70-80 CRI) and excellent (80+ CRI) color rendering properties is said to be “high quality light” because objects and people look more appealing, and the light level itself is perceived to be higher.

ELECTRONIC BALLAST – A ballast that utilizes electronic components to transform current at high frequency to operate fluorescent or discharge lamps.

FOOTCANDLE – The measurement of the amount of light reaching a surface. Footcandles are measured in lumens per square foot.

LAMP EFFICACY – Different lamp types have different abilities to convert electrical power (watts) into visible light (lumens). The quantity of light emitted (measured in lumens) is divided by the input power (watts) to determine the lamp’s efficacy. This is expressed as lumens per watt or LPW.

LED – The common abbreviation for light-emitting diode. Each individual LED consists of a semiconductor diode that emits light when a voltage is applied to it.

LIFE – How long on average a bulb is estimated to last (median life). The number of burning hours on average, after which 50% of large representative groups of lamps in laboratory tests, under controlled burning conditions and at a specified number of burning hours per start have failed.

LPW – Lumens per watt is a measure of energy efficiency. Fluorescent lamps are very energy efficient and emit up to 100 lumens per watt.

LUMENS – Bulb brightness. A higher number means brighter light. Fluorescent lamp lumens decrease over its life.

POWER FACTOR – The ratio of power (watts) to volt-amps of the ballast. The power factor ratio may be used to determine how efficiently total input power is being used. HPF ballasts require less AC current to do an optimum lighting job than would be required by an equivalent low power factor ballast. Additionally, fewer LPF fixtures can be installed in the circuit, increasing installation cost.

VOLTAGE – A measurement of electromotive force or the pressure of electricity. Typical residential construction is 120V @ 60Hz Typical commercial construction is 120V or 277V @ 60Hz

WATTAGE – A measurement of power.

Index

A

AAF	130
ACAF	143, 205
ADS	89
AELF	269
AGP	45
ALB	258
ALDF	137
ALNB	249
ALNV	173
ALS	108
ALV	184
ANF	147
ANP	56
APB	250
APF	144
APP	54
APS	87
APV	172
ARLS	109
ARLV	176
ARV	182
ASHF	126
ASHP	18, 21
ATL	268
ATLF	141, 268
ATV	171
AUF	212
AUW	233

B

BBF	154
BBV	190
BDWW	224
BEPL	51
BERF	207
BKNP	28
BLW	229
BMF	213
BMW	228
BOF	127
BONP	15, 17
BONV	170
BONW	215
BRS	111
BRW	237
BSSW	240
BTLW	241
BWNS	63
BWSW	245, 246

C

C2F	162
CAC	156
CAF	156
CALP	37
CAPW	239
CARF	204
CES	112
CEV	187
CFF	160
CHRF	198
CHS	75
CHV	183
CLAF	120
CLEP	35
CLKW	241
CLTW	220
CMB	263
CMF	161
CMNS	60

CNCW	216
COS	94
CRDL	277
CRRF	201
CSF	163
CVF	159
CYB	256
CZF	145
CZP	58
CZS	92

D

DIMCONTROL	298
DISF	197
DKTW	221
DWSW	240
DYP	52

E

ECHP	12
ECPS	114
EDS	90
EGRF	164
EGSF	165
ELEP	20
EL/LED	295
ES	295
EVNP	22
EVYW	238
EYELED	298

F

FR68	297
FTS	81, 180
FUF	155
FUS	110
FUV	186

G

GEPL	50
GLYS	84
GRAF	203

H

HAYB	248
HDB	262
HLWV	192
HRP	43
HVB	254
HZC	153

I

IDB	261
IDS	113
IDSS	117
IONS	64
ISLP	34

K

KB12	294, 297
KNLU	286
KNXW	219

L

LASW	218
LBTF	123
LCL	271
LCS	107
LCX	285, 292
LEDCC	298, 299
LENF	133
LGW	231
LMAF	149
LOLP	36
LSL	277
LW	274
LWL	273, 274, 276

M

MCF	142
MCP	55
MDRF	208
MHNP	27
MIDF	150
MIDS	96
MLAP	33
MNS	104
MQTB	253
MRF	151
MTRF	200
MXW	234

N

NLLP	288
NLS	103
NMBL	270
NPLS	97
NVS	85
NVV	85, 178
NWPW	242

O

OCFW	240
OTP	32
OTVF	136

P

PALS	70
PAXW	225
PCV	193
PEAF	134
PIDF	158
PLB	264
PLNS	114
PNTP	25
PRCL	273
PSDW	223
PSLED	298, 299
PSW	241
PTS	83

Q

QSSS	117
------	-----

R

R55-LED	297
RAB	255
RC	271
RDS	118
RFKIT	118, 166
RIS	188
RNS	77
RNV	177
RVEF	124
RVF	132
RWNS	67, 175
RWNW	211
RXYP	31
RYDV	169

S

S	279
SAF	146
SAP	57
SATW	242
SCC	295
SCTB	252
SDC	295
SEW	235
SHAL	272
SHB	259
SHC	152
SHS	101
SLB	257

SLDNP	39
SLF	139, 267
SLL	267
SNF	138
SNS	78
SNV	189
SORS	71
SPC	295
SPLE	285
SPLECL	285
SPLEDC	285
SPP	41
SPRL	272
SR45	299
SR68	299
SSP	47
ST	278
STCW	226
STICK2	294
STICK3	294
STICKPS	294, 297
STICK/TB	297
STLF	206
STMS	72
STN	279
SUF	148
SUMS	68
SXPL	49

T

T5L	290
T5LC	291
TAS	105
TBLED	298
TBLED/B	298
TPDW	244, 245
TPFW	245
TPUW	243
TPWW	243
TTMF	129
TYS	98

U

USS	117
-----	-----

V

V8PN	194
VIP	47
VNTS	116
VNTW	242
VNV	191
VTL	280

W

WAS	244
WCM	270
WES	91

X

XLC-CLIP	292
XLCC	292
XLCP	292
XLHB	292

Z

ZOS	95
ZUF	140, 266
ZUL	266

Photo credits:
Interior and Exterior Designs
VANGUARD Development

Sinclair Sconce
Hampton Inn
Waukegan, IL
John Schmuttenmaer


Brio Outdoor Sconce
LaQuinta Inn
Arlington Heights, IL
John Schmuttenmaer

©2019 AFX
All rights reserved.

Specifications subject to
change without notice.

Specific items may be
protected by patents
or patents pending.





2345 N. Ernie Krueger Circle • Waukegan, IL 60087

847.249.5970 • AFXinc.com

AFXCR0119