



















F617L-GM





**F739L-BN** • Brushed Nickel Finish • Silver Blades • White Lens

DC MOTOR **LED**

minkaAire®

# PANCAKE XL LED

with LED Light



F739L-WHF



F739L-DK



F739L-SL

## PANCAKE XL LED

with LED Light

A 62" version of our successful Pancake fan includes an integrated 20 watt LED light. Our Pancake XL LED ceiling fan magically houses all the necessary components of a high performance ceiling fan into the same slim body. Minimal, elegant and smooth, the profile is narrow, allowing for an unobtrusive, non-competing addition to any room. **Go big!**

### FEATURES

- 12° Blade Pitch • 4-Blades 62" Sweep • DC 188 x 14mm Motor • 6" Internally Threaded Downrod
- Max Ceiling Slope Angle 18° • 20W LED • 1300 Lumens • 80 CRI
- Special Hand Held Remote Control System Included - RC500

U.S. Patent(s): D750,215; D750,219, Additional U.S. Patent(s) Pending

### ENERGY INFORMATION\*\* (Excludes Lights)

- Airflow CFM: 6,500 • Electricity Used Watts: 38 • Airflow Efficiency CFM/Watts: 171

- F739L-SL** • Silver Finish • Silver Blades • White Lens
- F739L-WHF** • Flat White Finish • Flat White Blades • White Lens
- F739L-DK** • Distressed Koa Finish • Distressed Koa Blades • White Lens
- F739L-BN** • Brushed Nickel Finish • Silver Blades • White Lens

\*\* Estimated

\* LED (Light Emitting Diodes)  
See Page 12 for Pancake Family

# PANCAKE



F738-SL



F738-WHF



F738-DK



**F738-ORB**

## PANCAKE

Our Pancake ceiling fan magically houses all the needed components of a high performance ceiling fan in a slim 3-inch deep body. Minimal, elegant and smooth, the profile is narrow, allowing for an unobtrusive, non-competing addition to any room.

### FEATURES

- 12° Blade Pitch • 4-Blades 52" Sweep • 6" Internally Threaded Downrod
  - Max Ceiling Slope Angle 18° • Full Function Hand Held Remote Control System
- U.S. Patent(s): D750,215; D750,219, Additional U.S. Patent(s) Pending

### ENERGY INFORMATION (Excludes Lights)

- Airflow CFM: 5,405 • Electricity Used Watts: 63.9 • Airflow Efficiency CFM/Watts: 84.58

**F738-ORB** • Oil Rubbed Bronze Finish • Oil Rubbed Bronze Blades

**F738-SL** • Silver Finish • Silver Blades

**F738-WHF** • Flat White Finish • Flat White Blades

**F738-DK** • Distressed Koa Finish • Distressed Koa Blades



# SLIPSTREAM



F888-WHF




F888-DK



F888-ORB


*Shown with Cap for Non-Light Use*





**F886-84-BNW**

**F886-84-ORB**  
See Opposite Page



**F886-84-SI**  
Shown with optional  
K9886L-SI LED light kit

# XTREME H<sub>2</sub>O 84"

An outdoor version of one of our most popular large fan introductions, this industrial sized fan lends itself to any setting. Xtreme H<sub>2</sub>O's clean, sleek, contemporary design, complete with a DC motor and a choice of sizes, makes it perfect for large areas indoor or outdoor.

## FEATURES

- 4° Blade Pitch • 8-Blades 84" Sweep • DC 123 x 30mm Motor
- 6" Downrod • Aluminum Blades • Install with Blades at least 10' above the Floor
- Special Hand Held Remote Control System Included - RC400
- Custom 20W LED Light Kit K9886L Available (Sold Separately Page(s): 275)
- Indoor/Outdoor Use UL Listed for Wet Locations

U.S. Patent(s): Pending

## ENERGY INFORMATION\*\* (Excludes Lights)

- Airflow CFM: 12,209 • Electricity Used Watts: 31 • Airflow Efficiency CFM/Watts: 393.9

**F886-84-ORB** • Oil Rubbed Bronze • Oil Rubbed Bronze Blades

**F886-84-BNW** • Brushed Nickel Wet Finish • Silver Blades

**F886-84-SI** • Smoked Iron Finish • Smoked Iron Blades

\*\* Estimated  
\* LED (Light Emitting Diodes)





# XTREME H<sub>2</sub>O




**F886-65-ORB**  
Shown with optional  
K9886L-ORB LED light kit



**F886-65-WHF**  
Shown with optional  
K9886L-WHF LED light kit





# XTREME

This industrial size fan lends itself to almost any setting. Xtreme’s clean, sleek, contemporary design with a DC motor and a choice of sizes makes it perfect for large areas.

## FEATURES

- 4° Blade Pitch • 9-Blades 72", 80", 88" or 96" Sweep • DC 165 x 25mm Motor
- 6" Downrod • Aluminum Blades • Install with Blades at least 10' above the Floor
- Special Hand Held Remote Control System Included - RC400

## ENERGY INFORMATION FOR 72" (Excludes Lights)

- Airflow CFM: 10,203 • Electricity Used Watts: 29 • Airflow Efficiency CFM/Watts: 352

## ENERGY INFORMATION FOR 80" (Excludes Lights)

- Airflow CFM: 10,298 • Electricity Used Watts: 30 • Airflow Efficiency CFM/Watts: 343.3


## ENERGY INFORMATION FOR 88" (Excludes Lights)

- Airflow CFM: 12,209 • Electricity Used Watts: 31 • Airflow Efficiency CFM/Watts: 393.9

## ENERGY INFORMATION FOR 96" (Excludes Lights)

- Airflow CFM: 13,080 • Electricity Used Watts: 30.5 • Airflow Efficiency CFM/Watts: 428.9

- F887-72-BN 72"** • Brushed Nickel Finish • Silver Blades
- F887-80-BN 80"** • Brushed Nickel Finish • Silver Blades
- F887-88-BN 88"** • Brushed Nickel Finish • Silver Blades
- F887-96-BN 96"** • Brushed Nickel Finish • Silver Blades




# XTREME

F887-72-BN 72"  
F887-80-BN 80"  
F887-88-BN 88" (Shown)  
F887-96-BN 96"

F887-72-ORB 72"  
F887-80-ORB 80"  
F887-88-ORB 88"  
F887-96-ORB 96"  
*See Next Page*



# XTREME



- F887-72-ORB 72"**
- F887-80-ORB 80"**
- F887-88-ORB 88" *(Shown)***
- F887-96-ORB 96"**

- F887-72-BN 72"**
- F887-80-BN 80"**
- F887-88-BN 88"**
- F887-96-BN 96"**
- See Previous Page*





# NINETY-NINE

with LED Light



**F899L-ORB**

**F899L-DK**  
*See Previous Page*

# NINETY-NINE

with LED Light

Minka-Aire® introduces our Ninety-Nine fan, featuring a total of 99 inches in diameter! A refreshing transitional design featuring 9-blades, 26 watt LED\* and a DC motor. Ideal for residential and commercial use. Includes a six speed hand held remote control and is reversible for winter and summer.

## FEATURES

- Variable Blade Pitch • 9-Blades 99" Sweep • DC 172 x 25mm Motor • 6" Downrod
- Special Hand Held Remote Control System Included - RC600
- Integrated LED Light Uses 26W LED (Included) 3 Year Warranty • 1,899 Lumens • 2,700K • CRI 81

U.S. Patent(s): Pending

## ENERGY INFORMATION (Excludes Lights)

- Airflow CFM: 13,350 • Electricity Used Watts: 45 • Airflow Efficiency CFM/Watts: 295

**F899L-ORB** • Oil Rubbed Bronze Finish • Toned Tobacco Blades • Etched Opal Glass

**F899L-BN/SL** • Brushed Nickel Finish • Silver Blades • Etched Opal Glass

**F899L-DK** • Distressed Koa Finish • Distressed Koa Blades • Etched Opal Glass



F899L-BN/SL









**F803-LN**

## ARTEMIS™

**F803-LN** • Liquid Nickel Finish • Etched Opal Glass  
**F803-MG** • Mahogany Finish • Etched Opal Glass  
**F803-CPBR** • Copper Bronze Finish • Tinted Opal Glass  
**F803-SL** • Silver Finish • Etched Opal Glass



F803-MG



F803-CPBR



F803-SL



F803-MP

## ARTEMIS™

**F803-MP** • Maple Finish • Etched Opal Glass  
**F803-TL** • Translucent Finish • Etched Opal Glass  
**F803-BK** • High Gloss Black Finish • Etched Opal Glass  
**F803-WH** • High Gloss White Finish • Etched Opal Glass

# ARTEMIS™



F803-TL



F803-BK



F803-WH

























































































































**F594-PW**



**F594-WH**

**F594-ORB**  
*See Opposite Page*

## TRADITIONAL CONCEPT™ 52"

A variation on our best selling contemporary Concept™ II fan, this fan provides the same superb styling for your more traditional indoor and outdoor settings.

### FEATURES

- 14° Blade Pitch • 3-Blades 52" Sweep
- Flush Mount - Ideal for Low Ceilings Total Hanging Depth 10¾" Drop from Ceiling
- Full Function Wall Control System
- Integrated Halogen Light Uses 1-100W Mini-Can Halogen Bulb (Included)
- Indoor/Outdoor Use UL Listed for Wet Locations • Cap for Non-Light Use (Included)

### ENERGY INFORMATION (Excludes Lights)

- Airflow CFM: 6,565 • Electricity Used Watts: 60.5 • Airflow Efficiency CFM/Watts: 108.58

**F594-ORB** • Oil Rubbed Bronze Finish • Medium Maple Blades • Tinted Opal Glass

**F594-PW** • Pewter Finish • Dark Maple Blades • Opal Glass

**F594-WH** • White Finish • White Blades • Opal Glass





**F593-PW**

## TRADITIONAL CONCEPT™ 44"

A variation on our best selling contemporary Concept™ II fan, this fan provides the same superb styling for your more traditional indoor and outdoor settings.

### **FEATURES**

- 14° Blade Pitch • 3-Blades 44" Sweep
- Flush Mount - Ideal for Low Ceilings Total Hanging Depth 10¾" Drop from Ceiling
- Full Function Wall Control System
- Integrated Halogen Light Uses 1-100W Mini-Can Halogen Bulb (Included)
- Indoor/Outdoor Use UL Listed for Wet Locations • Cap for Non-Light Use (Included)

### **ENERGY INFORMATION** (Excludes Lights)

- Airflow CFM: 4,940 • Electricity Used Watts: 49 • Airflow Efficiency CFM/Watts: 100

**F593-PW** • Pewter Finish • Dark Maple Blades • Opal Glass

**F593-ORB** • Oil Rubbed Bronze Finish • Medium Maple Blades • Tinted Opal Glass

**F593-WH** • White Finish • White Blades • Opal Glass

# TRADITIONAL CONCEPT™ 44"



**F593-ORB**



**F593-WH**  
*Shown with Cap for Non-Light Use*





F824-ORB/TB

うちわ

## UCHIWA

Harmoniously marked by characteristics and finishes of the present period, the Uchiwa is a functional art piece.

### FEATURES

- 16° Blade Pitch • 3-Blades 56" Sweep • 6" Downrod • Full Function Wall Control System
- Integrated Halogen Light Uses 1-75W Mini-Can Halogen Bulb (Included)

U.S. Patent(s): D618,786; D618,787; D620,586

### ENERGY INFORMATION (Excludes Lights)

- Airflow CFM: 4,574 • Electricity Used Watts: 58 • Airflow Efficiency CFM/Watts: 78.86

- F824-ORB/TB** • Oil Rubbed Bronze / Toned Brass Finish • Oil Rubbed Bronze Blades • Tinted Opal Glass
- F824-BK/CH** • Black / Chrome Finish • Silver Blades • Etched Opal Glass
- F824-WH** • White Finish • White Blades • Etched Opal Glass

# UCHIWA



**F824-BK/CH**



**F824-WH**



**F596-BN**

## CIRQUE™

Winner of the 2003 Chicago Athenaeum: Museum of  
Architecture and Design's Good Design Award

### FEATURES

- 14° Blade Pitch • 3-Blades 54" Sweep and 3-Blades 25" Sweep • 6" Downrod
- Full Function Wall Control System
- Integrated Halogen Light Uses 1-50W MR16 120V 2-Pin Halogen Bulb (Included)
- Cap for Non-Light Use (Included)

U.S. Patent(s): D510,621; D513,316; D514,689; D524,433; D549,816

Accessory Blades Available. See Page(s): 288

### ENERGY INFORMATION (Excludes Lights)

- Airflow CFM: 5,087 • Electricity Used Watts: 49 • Airflow Efficiency CFM/Watts: 103.81

**F596-BN** • Brushed Nickel Finish • Silver Blades • Etched Glass

**F596-PN/TL** • Polished Nickel Finish • Translucent Blades • Etched Glass



**F596-PN/TL**



**F596-BN**  
*Shown with Optional FB196-RYB Blades*



**F596-BN**  
*Shown with Optional FB196-MG Blades*

# ZEN



**F514-WH**



**F514-BN**  
*Shown with Cap for Non-Light Use*



**F514-ORB**

## ZEN

A clean modern profile is accentuated in three finish options.

### FEATURES

- 14° Blade Pitch • 4-Blades 52" Sweep • 6" Downrod
- Full Function Hand Held Remote Control System
- Integrated Light Kit Uses 2-13W Non-Dimmable GU24 CFL Bulbs (Included)
- Cap for Non-Light Use (Included)

### ENERGY INFORMATION (Excludes Lights)

- Airflow CFM: 6,148 • Electricity Used Watts: 71 • Airflow Efficiency CFM/Watts: 86.05

**F514-ORB** • Oil Rubbed Bronze Finish • Medium Maple Blades • Tinted Opal Glass

**F514-WH** • White Finish • White Blades • White Frosted Glass

**F514-BN** • Brushed Nickel Finish • Silver Blades • White Frosted Glass



**F513-BN**

## NEW ERA

Traditional in styling, yet defined by simple, soft lines.

### FEATURES

- 14° Blade Pitch • 4-Blades 52" Sweep • 6" Downrod
- Full Function Hand Held Remote Control System
- ENERGY STAR® Light Kits Available (Part #K9380-1 and #K9380-2 Page(s): 267)

### ENERGY INFORMATION (Excludes Lights)

- Airflow CFM: 6,230 • Electricity Used Watts: 73 • Airflow Efficiency CFM/Watts: 85.25

**F513-BN** • Brushed Nickel Finish • Dark Walnut Blades

**F513-WH** • White Finish • White Blades

**F513-KA** • Kocoa Finish • Reversible Toned Medium Maple / Dark Maple Blades

**F513-ORB** • Oil Rubbed Bronze Finish • Medium Maple Blades

# NEW ERA



**F513-WH**



**F513-KA**

*Shown with Toned Medium Maple Blades  
Reversible to Dark Maple Blades*



**F513-ORB**





**F598-ORB**

## AIRUS™

Airus™ is poetry in motion. Its graceful silhouette comfortably fits in any transitional setting. Featured uplight can be controlled independently of the halogen light below.

### FEATURES

- 14° Blade Pitch • 5-Blades 54" Sweep • 6" Downrod
- Full Function Wall Control System Independent Up/Downlight
- Integrated Halogen Uplight Uses 2-50W Mini-Can Halogen Bulbs (Included)
- Integrated Halogen Downlight Uses 2-50W Mini-Can Halogen Bulbs (Included)

U.S. Patent(s): D471,269; D473,639; D475,776

### ENERGY INFORMATION (Excludes Lights)

- Airflow CFM: 5,668 • Electricity Used Watts: 82 • Airflow Efficiency CFM/Watts: 69.12

**F598-ORB** • Oil Rubbed Bronze Finish • Medium Maple Blades • Excavation Glass

**F598-WH** • White Finish • High Gloss White Blades • Acid Etched Glass

**F598-BN** • Brushed Nickel Finish • Silver Blades • Acid Etched Glass



F598-WH



F598-BN



F802-PN

## VINTAGE GYRO™

An addition to our popular Gyro™ family, the Vintage Gyro™ performs with the same efficiency and unsurpassed level of comfort as our other Gyro™ models, but with an early 20<sup>th</sup> Century style.

### FEATURES

- High Performance Twin Turbofans Total Sweep 42" • 20° Blade Pitch • 6" Downrod
- 720 - 1,350 R.P.M. Fan Speeds • Turbofan Heads Adjustable Up and Down
- Complete Assembly Rotates 360° at 3 R.P.M.
- Full Function Wall Control System Incorporating Fully Independent Fan Head Speeds and Axis Rotation
- Integrated Halogen Light Uses 1-100W Mini-Can Halogen Bulb (Included)
- Cap for Non-Light Use (Included)

U.S. Patent(s): 6,832,902; 7,183,680; 7,229,255

### ENERGY INFORMATION (Excludes Lights)

- Airflow CFM: 5,050 • Electricity Used Watts: 102 • Airflow Efficiency CFM/Watts: 49.51

- F802-PN** • Polished Nickel Finish • Rosewood Blades • Etched Opal Glass  
**F802-ORB** • Oil Rubbed Bronze Finish • Oil Rubbed Bronze Blades • Tinted Opal Glass  
**F802-BN/CH** • Brushed Nickel / Chrome Finish • Rosewood Blades • Etched Opal Glass  
**F802-KA** • Kocoa Finish • Kocoa Blades • Tinted Opal Glass

# VINTAGE GYRO™



F802-ORB



F802-BN/CH



F802-KA





F502-BCW

## TRADITIONAL GYRO™

A magnificent rendition of the original Gyro™ design, the traditional finish transcends the turns of time.

### FEATURES

- High Performance Twin Turbofans Total Sweep 42" • 20° Blade Pitch • 4½" and 12" Downrod
- 720 - 1,350 R.P.M. Fan Speeds • Turbofan Heads Adjustable Up and Down
- Complete Assembly Rotates 360° at 3 R.P.M.
- Full Function Wall Control System Incorporating Fully Independent Fan Head Speeds and Axis Rotation
- Integrated Halogen Light Uses 1-100W Mini-Can Halogen Bulb (Included)
- Cap for Non-Light Use (Included)

U.S. Patent(s): D523,548; D523,549; D523,550; D523,983; D524,438; D526,059; D526,400; D526,712; D530,810; D532,097; D567,350; 6,832,902; 7,183,680; 7,229,255 © 2004 Minka Lighting, Inc.

### ENERGY INFORMATION (Excludes Lights)

- Airflow CFM: 5,050 • Electricity Used Watts: 102 • Airflow Efficiency CFM/Watts: 49.51

**F502-BCW** • Belcaro Walnut™ Finish • Belcaro Walnut™ Blades • Belcaro Walnut™ Glass



**F602-BN/CH**



**F602-RRB**

## GYRO™

A truly unique design offering an unsurpassed level of comfort. The Gyro™ fan's ability to precisely control the direction and intensity of the cooling breeze efficiently circulates air in any environment.

### FEATURES

- High Performance Twin Turbofans Total Sweep 42" • 20° Blade Pitch • 6" Downrod
- 720 - 1,350 R.P.M. Fan Speeds • Turbofan Heads Adjustable Up and Down
- Complete Assembly Rotates 360° at 3 R.P.M.
- Full Function Wall Control System Incorporating Fully Independent Fan Head Speeds and Axis Rotation
- Integrated Halogen Light Uses 1-100W Mini-Can Halogen Bulb (Included)
- Cap for Non-Light Use (Included)

U.S. Patent(s): D478,975; D489,443, D490,146; 6,832,902; 7,183,680; 7,229,255

### ENERGY INFORMATION (Excludes Lights)

- Airflow CFM: 5,050 • Electricity Used Watts: 102 • Airflow Efficiency CFM/Watts: 49.51


**F602-BN/CH** • Brushed Nickel / Chrome Finish with Chrome Accents and Cages • Rosewood Blades • Etched Opal Glass  
**F602-RRB** • Restoration Bronze™ Finish • Restoration Bronze™ Blades • Etched Opal School House Globe Glass

# GYRO™ WET



F402-ORB





**F402-BNW**  
Shown with Cap for Non-Light Use

## GYRO™ WET

Capturing the design elements of the original Gyro™, the Gyro™ Wet provides unsurpassed performance and comfort levels in the toughest environments. Rotating 360°, and controlled by a wall control system, it offers wonderful cooling in any area and the option to stop and redirect air for maximum benefit.

### FEATURES

- High Performance Twin Turbofans Total Sweep 42" • 20° Blade Pitch
- Complete Assembly Rotates 360° at 3 R.P.M. • 720 - 1,350 R.P.M. Fan Speeds
- Turbofan Heads Adjustable Up and Down • Galvanized Steel 6" Downrod
- Full Function Wall Control System Incorporating Fully Independent Fan Head Speeds and Lighting Fixture
- Integrated Halogen Light Uses 1-100W Mini-Can Halogen Bulb (Included)
- Cap for Non-Light Use (Included) • Indoor/Outdoor Use UL Listed for Wet Locations

U.S. Patent(s): D478,975; D489,443; D489,809; D490,146; 6,832,902; 7,183,680; 7,229,255

### ENERGY INFORMATION (Excludes Lights)

- Airflow CFM: 4,082 • Electricity Used Watts: 108 • Airflow Efficiency CFM/Watts: 38

**F402-ORB** • Oil Rubbed Bronze Finish • Oil Rubbed Bronze Blades • Etched Opal School House Globe Glass  
**F402-BNW** • Brushed Nickel Wet Finish • Silver Blades • Etched Opal Glass





**F306L-BS/SL**

**F306L-ORB/MM**  
See Opposite page

## ELEMENTAL GYRO™ with LED Light

Elemental Gyro™ is the newest addition to our Gyro™ series. A clean, industrial spirit combined with a LED\* light source and etched opal glass. The Gyro™ series continues to offer air movement throughout the entire room, or can be stopped to position air in only one area. Adjustable fan cages further enhance air movement.

### FEATURES

- High Performance Twin Turbofans Total Sweep 42" • 23° Blade Pitch • 6" Downrod
  - 800 - 1,470 R.P.M. Fan Speeds • Turbofan Heads Adjustable Up and Down
  - Complete Assembly Rotates 360° at 3 R.P.M.
  - Full Function Wall Control System Incorporating Fully Independent Fan Head Speeds and Axis Rotation
  - Integrated LED Light Uses 16W LED (Included) 3 Year Warranty • 1,352 Lumens • 2,700K • CRI 80
- U.S. Patent(s): 6,832,902; 7,183,680; 7,229,255 Additional U.S. Patent(s) Pending

### ENERGY INFORMATION (Excludes Lights)

- Airflow CFM: 4,082 • Electricity Used Watts: 108 • Airflow Efficiency CFM/Watts: 38

**F306L-ORB/MM** • Oil Rubbed Bronze Finish • Medium Maple Blades • Etched Opal Glass  
**F306L-BN/SL** • Brushed Steel Finish • Silver Blades • Etched Opal Glass



**F304L-BN/SL**



**F304L-ORB/MM**

## CAGE FREE GYRO™

with LED Light

A wonderful addition to our Gyro™ series. Simple, clean design featuring twin turbo fans, 16 watt LED\* and cage free blades allow for a classic transitional spirit.

### FEATURES

- High Performance Twin Turbofans Total Sweep 37" • 23° Blade Pitch • 6" Downrod
- 800 - 1,470 R.P.M. Fan Speeds • Turbofan Heads Adjustable Up and Down
- Complete Assembly Rotates 360° at 3 R.P.M.
- Full Function Wall Control System Incorporating Fully Independent Fan Head Speeds and Axis Rotation
- Integrated LED Light Uses 16W LED (Included) 3 Year Warranty • 1,352 Lumens • 2,700K • CRI 80

U.S. Patent(s): 6,832,902; 7,183,680; 7,229,255 Additional U.S. Patent(s) Pending

### ENERGY INFORMATION (Excludes Lights)

- Airflow CFM: 2,726 • Electricity Used Watts: 107 • Airflow Efficiency CFM/Watts: 25

**F304L-BN/SL** • Brushed Nickel Finish • Silver Blades • Etched Opal Glass

**F304L-ORB/MM** • Oil Rubbed Bronze Finish • Medium Maple Blades • Etched Opal Glass



**F302-RRB**



**F302-BN**

## GYRETTE™

The Gyrette™ captures the design elements of the original Gyro™ in a smaller format. We have utilized flexible arms to maximize air circulation.

### FEATURES

- High Performance Twin Turbofans Total Sweep 36" • Adjustable Turbofan Heads • 14° Blade Pitch
- Complete Assembly Rotates 360° at 3 R.P.M. • 3-Speeds: 800, 1,090, 1,470 R.P.M.
- 30° Flexible Arms • 6" Downrod • Full Function Hand Held Remote Control System

### ENERGY INFORMATION (Excludes Lights)

- Airflow CFM: 1,480 • Electricity Used Watts: 58 • Airflow Efficiency CFM/Watts: 25.52

- F302-RRB** • Restoration Bronze™ Finish • Restoration Bronze™ Blades
- F302-BN** • Brushed Nickel Finish • Brushed Nickel Blades



F852L-HBZ

## ALVA

with LED Light

Inspired by a great American inventor, Alva merges technology and history in a transitional design of timeless aesthetic value. With five Dark Walnut Solid Wood Blades and three medium base LED ferro bulbs, it will bring comfort and a refreshing look to your home or office.

### FEATURES

- 14° Blade Pitch • 5-Blades 56" Sweep • DC 120 x 15mm Motor • 6" Downrod
- Integrated Light Uses 3-6W LED Medium Base Ferro Bulb (Included)
- Hand Held Remote - RC500

U.S. Patent(s): Pending

### ENERGY INFORMATION\*\* (Excludes Lights)

- Airflow CFM: 6,000 • Electricity Used Watts: 30 • Airflow Efficiency CFM/Watts: 200

**F852L-HBZ** • Heirloom Bronze Finish • Aged Boardwalk Blades

**F852L-BN** • Brushed Nickel Finish • Seashore Grey Blades

**F852L-TI** • Tarnished Iron Finish • Dark Walnut Blades

ALVA  
with LED Light



F852L-BN



F852L-TI

LED DC MOTOR



**F539-BNK**

**FEATURES**

- 14° Blade Pitch • 5-Blades 72" Sweep • 6" Downrod • Full Function Wall Control System
- Universal Light Kit Adaptable (Sold Separately. See K9376-1 and K9376-2 on Page(s): 267)
- Quick Connect Switch Cup

**ENERGY INFORMATION** (Excludes Lights)


- Airflow CFM: 9,071 • Electricity Used Watts: 106 • Airflow Efficiency CFM/Watts: 85.36

**F539-BNK** • Burnished Nickel Finish • Seashore Grey Blades



## GREAT ROOM TRADITIONAL

Great Room interiors require new ways to manage air. We have accomplished this with expanded blade spans, larger motors and enhanced housings in styles designed to complement those rooms.



F539-HBZ

## GREAT ROOM TRADITIONAL

Great Room interiors require new ways to manage air. We have accomplished this with expanded blade spans, larger motors and enhanced housings in styles designed to complement those rooms.

### FEATURES

- 14° Blade Pitch • 5-Blades 72" Sweep • 6" Downrod • Full Function Wall Control System
- Universal Light Kit Adaptable (Sold Separately. See K9376-1 and K9376-2 on Page(s): 267)
- Quick Connect Switch Cup

### ENERGY INFORMATION (Excludes Lights)

- Airflow CFM: 9,071 • Electricity Used Watts: 106 • Airflow Efficiency CFM/Watts: 85.36

**F539-HBZ** • Heirloom Bronze Finish • Aged Boardwalk Blades

**F539-BN** • Brushed Nickel Finish • Dark Walnut Blades

**F539-BCW** • Belcaro Walnut™ Finish • Dark Walnut Blades

**F539-ORB** • Oil Rubbed Bronze Finish • Dark Walnut Blades

**F539-BNK** • Burnished Nickel Finish • Seashore Grey Blades

# GREAT ROOM TRADITIONAL



F539-BN



F539-BCW



F539-ORB



**F701-PW**



**F701-DRF**



**F701-KA**  
*Shown with Toned Medium Maple Blades  
Reversible to Dark Walnut Blades*



**F701-DRB**



**F701-PN**

## DELANO®

### FEATURES

- 14° Blade Pitch • 5-Blades 52" Sweep • 6" Downrod
- Wall Control System Independent Up/Downlight
- Integrated Uplight Use 6-15W Candelabra Bulbs (Included)
- Integrated Halogen Downlight Uses 2-50W Mini-Can Halogen Bulbs (Included)

### ENERGY INFORMATION (Excludes Lights)

- Airflow CFM: 5,278 • Electricity Used Watts: 72 • Airflow Efficiency CFM/Watts: 73.31

**F701-PN** • Polished Nickel Finish • Silver Blades • White Frosted Glass

**F701-PW** • Pewter Finish • Natural Walnut Blades • Etched Marble Glass

**F701-DRF** • Driftwood Finish • Driftwood Blades • Bone White Glass

**F701-KA** • Kocoa Finish • Reversible Toned Medium Maple / Dark Walnut Blades • Rustic Scavo Glass

**F701-DRB** • Dark Restoration Bronze™ Finish • Dark Walnut Blades • Rustic Scavo Glass



F711-DRB

## DELANO® II

Inspired by a long-time favorite, the Delano® II offers the same clean, neo-transitional look but with less than an 11-inch drop from the ceiling.

### FEATURES

- 14° Blade Pitch • 5-Blades 52" Sweep
- Flush Mount - Ideal for Low Ceilings Less than 11" Drop from Ceiling
- Full Function Wall Control System
- Integrated Halogen Light Uses 2-50W Mini-Can Halogen Bulbs (Included)

U.S. Patent(s): D595,403; D597,655

### ENERGY INFORMATION (Excludes Lights)

- Airflow CFM: 5,634 • Electricity Used Watts: 70 • Airflow Efficiency CFM/Watts: 80.49

- F711-DRB** • Dark Restoration Bronze™ Finish • Dark Walnut Blades • Rustic Scavo Glass  
**F711-PN** • Polished Nickel Finish • Silver Blades • White Frosted Glass  
**F711-PW** • Pewter Finish • Natural Walnut Blades • Etched Marble Glass

# DELANO<sup>®</sup> II



F711-PN



F711-PW



**F614-HBZ**

**FEATURES**

- 14° Blade Pitch • 5-Blades 54" Sweep • 6" Downrod • 3-Speed Pull Chain
- Custom Light Kit Adaptable (Sold Separately. Page(s): 267)

**ENERGY INFORMATION** (Excludes Lights)

- Airflow CFM: 6,257 • Electricity Used Watts: 70.5 • Airflow Efficiency CFM/Watts: 89

**F614-HBZ** • Heirloom Bronze Finish • Aged Boardwalk Blades



## TIMELESS

A smooth blend of finish and form distinguishes the Timeless fan, enhanced by simple clean lines and a unique blade iron design.

F614-BNK





**F614-MCG**



**F614-DBB**

**F614-BNK**  
See Opposite Page

## TIMELESS

A smooth blend of finish and form distinguishes the Timeless fan, enhanced by simple clean lines and a unique blade iron design.

### FEATURES

- 14° Blade Pitch • 5-Blades 54" Sweep • 6" Downrod • 3-Speed Pull Chain
- Custom Light Kit Adaptable (Sold Separately. Page(s): 267)

### ENERGY INFORMATION (Excludes Lights)

- Airflow CFM: 6,257 • Electricity Used Watts: 70.5 • Airflow Efficiency CFM/Watts: 89

**F614-BNK** • Burnished Nickel Finish • Seashore Grey Blades

**F614-MCG** • Mottled Copper with Gold Highlights Finish • Dark Walnut Blades

**F614-DBB** • Dark Brushed Bronze Finish • Dark Maple Blades

**F614-HBZ** • Heirloom Bronze Finish • Aged Boardwalk Blades





F614-PW

## TIMELESS

**F614-PW** • Pewter Finish • Dark Walnut Blades  
**F614-ORB** • Oil Rubbed Bronze Finish • Medium Maple Blades  
**F614-FB** • French Beige Finish • Medium Maple Blades  
**F614-PI** • Patina Iron Finish • Dark Maple Blades

# TIMELESS



F614-ORB



F614-FB



F614-PI



F689-KA

## KOLA-XL

The Kola-XL 60-inch fan features the same design elements as the Kola 52-inch. It has been upgraded to provide the performance necessary for larger rooms and has the convenience of a remote control system.

### FEATURES

- 12° Blade Pitch • 60" 5-Blades • 6" Downrod
- Full Function Hand Held Remote Control System
- Universal Light Kit Adaptable (Sold Separately. Page(s): 267)

### ENERGY INFORMATION (Excludes Lights)

- Airflow CFM: 7,557 • Electricity Used Watts: 84.6 • Airflow Efficiency CFM/Watts: 89

**F689-KA** • Kocoa Finish • Reversible Toned Medium Maple / Dark Maple Blades

**F689-WH** • White Finish • White Blades

**F689-DBB** • Dark Brushed Bronze Finish • Reversible Dark Maple / Dark Walnut Blades

**F689-PW** • Pewter Finish • Reversible Dark Maple / Dark Walnut Blades

# KOLA-XL



F689-WH



F689-DBB



F689-PW





**F688-PW**

*Shown with Dark Maple Blades  
Reversible to Dark Walnut Blades*

## KOLA

Smooth lines with a sleek blade iron design and a robust body make the Kola a perfect complement to any home décor.

**FEATURES**

- 12° Blade Pitch • 5-Blades 52" Sweep • 6" Downrod • 3-Speed Pull Chain
- Universal Light Kit Adaptable (Sold Separately. Page(s): 267)

**ENERGY INFORMATION** (Excludes Lights)

- Airflow CFM: 6,002 • Electricity Used Watts: 71.3 • Airflow Efficiency CFM/Watts: 84

**F688-PW** • Pewter Finish • Reversible Dark Maple / Dark Walnut Blades

**F688-WH** • White Finish • White Blades

**F688-DBB** • Dark Brushed Bronze Finish • Reversible Dark Maple / Dark Walnut Blades

**F688-KA** • Kocoa Finish • Reversible Toned Medium Maple / Dark Maple Blades



**F688-WH**



**F688-DBB**

*Shown with Dark Walnut Blades  
Reversible to Dark Maple Blades*



**F688-KA**

*Shown with Toned Medium Maple Blades  
Reversible to Dark Maple Blades*





**F696-HBZ**

**FEATURES**

- 12° Blade Pitch • 5-Blades 60" Sweep • 6" Downrod
- Full Function Hand Held Remote Control System
- Universal Light Kit Adaptable (Sold Separately. Page(s): 267)

**ENERGY INFORMATION** (Excludes Lights)

- Airflow CFM: 7,557 • Electricity Used Watts: 84.6 • Airflow Efficiency CFM/Watts: 89

**F696-HBZ** • Heirloom Bronze Finish • Aged Boardwalk Blades



## KAFÉ-XL

Simple elegance defined in rich finishes, the Kafé-XL brings an exciting look with enhanced features to our value collection.



**F696-BNK**

## KAFÉ-XL

Simple elegance defined in rich finishes, the Kafé-XL brings an exciting look with enhanced features to our value collection.

### FEATURES

- 12° Blade Pitch • 5-Blades 60" Sweep • 6" Downrod
- Full Function Hand Held Remote Control System
- Universal Light Kit Adaptable (Sold Separately. Page(s): 267)

### ENERGY INFORMATION (Excludes Lights)

- Airflow CFM: 7,557 • Electricity Used Watts: 84.6 • Airflow Efficiency CFM/Watts: 89

**F696-BNK** • Burnished Nickel Finish • Seashore Grey Blades

**F696-WH** • White Finish • White Blades

**F696-VP** • Vineyard Patina Finish • Reversible Dark Maple / Dark Walnut Blades

**F696-KA** • Kocoa Finish • Reversible Toned Medium Maple / Dark Maple Blades

**F696-CC** • Cognac Finish • Reversible Natural Walnut / Dark Walnut Blades

**F696-HBZ** • Heirloom Bronze Finish • Aged Boardwalk Blades

# KAFÉ-XL



**F696-WH**



**F696-VP**

*Shown with Dark Walnut Blades  
Reversible to Dark Maple Blades*



**F696-KA**

*Shown with Toned Medium Maple Blades  
Reversible to Dark Maple Blades*



**F696-CC**

*Shown with Natural Walnut Blades  
Reversible to Dark Walnut Blades*





**F695-BNK**

**FEATURES**

- 12° Blade Pitch • 5-Blades 52" Sweep • 6" Downrod • 3-Speed Pull Chain
- Universal Light Kit Adaptable (Sold Separately. Page(s): 267)

**ENERGY INFORMATION** (Excludes Lights)

- Airflow CFM: 6,002 • Electricity Used Watts: 71.3 • Airflow Efficiency CFM/Watts: 84

**F695-BNK** • Burnished Nickel Finish • Seashore Grey Blades



## KAFÉ

Simple yet elegant in several finishes, the Kafé brings a refreshing look to our transitional collection.



**F695-HBZ**

## KAFÉ

Simple yet elegant in several finishes, the Kafé brings a refreshing look to our transitional collection.

### FEATURES

- 12° Blade Pitch • 5-Blades 52" Sweep • 6" Downrod • 3-Speed Pull Chain
- Universal Light Kit Adaptable (Sold Separately. Page(s): 267)

### ENERGY INFORMATION (Excludes Lights)

- Airflow CFM: 6,002 • Electricity Used Watts: 71.3 • Airflow Efficiency CFM/Watts: 84

**F695-HBZ** • Heirloom Bronze Finish • Aged Boardwalk Blades

**F695-CC** • Cognac Finish • Reversible Natural Walnut / Dark Walnut Blades

**F695-WH** • White Finish • White Blades

**F695-VP** • Vineyard Patina Finish • Reversible Dark Maple / Dark Walnut Blades

**F695-KA** • Kocoa Finish • Reversible Toned Medium Maple / Dark Maple Blades

**F695-BNK** • Burnished Nickel Finish • Seashore Grey Blades



**F695-CC**  
*Shown with Natural Walnut Blades  
Reversible to Dark Walnut Blades*



**F695-WH**



**F695-VP**  
*Shown with Dark Maple Blades  
Reversible to Dark Walnut Blades*



**F695-KA**  
*Shown with Toned Medium Maple Blades  
Reversible to Dark Maple Blades*





F620-BN

## BOLO™

Four of our best selling finishes accent this fan, creating a decorative alternative to an everyday need. Includes glass bowl light kit and remote control system.

### FEATURES

- 14° Blade Pitch • 5-Blades 52" Sweep • 6" Downrod • Hand Held Remote Control System
- Bowl Light Kit Uses 3-60W Candelabra Bulbs (Included) • Cap for Non-Light Use (Included)

### ENERGY INFORMATION (Excludes Lights)

- Airflow CFM: 5,712 • Electricity Used Watts: 74 • Airflow Efficiency CFM/Watts: 77.19

- F620-BN** • Brushed Nickel Finish • Dark Walnut Blades • Etched Swirl Glass
- F620-DBB** • Dark Brushed Bronze Finish • Dark Maple Blades • Avorio Mezzo™ Glass
- F620-BCW** • Belcaro Walnut™ Finish • Dark Walnut Blades • Excavation Glass
- F620-ORB** • Oil Rubbed Bronze Finish • Medium Maple Blades • Excavation Glass



F620-DBB



F620-BCW



F620-ORB



F820-CT



F820-IBR



## SANTA LUCIA™

### FEATURES

- 14° Blade Pitch • 5-Blades 60" Sweep • 6" Downrod
- Full Function Wall Control System with Independent Up/Downlight Control
- Integrated Uplight Uses 5-15W Candelabra Bulbs (Included)
- Integrated Halogen Downlight Uses 2-50W Mini-Can Halogen Bulbs (Included)

U.S. Patent(s): D556,882; D559,436; D568,984; D570,986; D574,948; D599,000; D599,466; 5,554,006

© 2006 Minka Lighting, Inc.

### ENERGY INFORMATION (Excludes Lights)

- Airflow CFM: 6,936.7 • Electricity Used Watts: 84 • Airflow Efficiency CFM/Watts: 82.58

**F820-CT** • Cattera Bronze™ Finish • Dark Walnut Blades • with Cognac Fluted Etched Glass

**F820-IBR** • Illuminati Bronze™ Finish • Dark Walnut Blades • with Silver Patina Glass

**CM8222-IBR 22"** • Illuminati Bronze™ Finish • 22" Diameter • Matching Ceiling Medallion for F820-IBR



CM8222-IBR 22"

© 2005 Minka Lighting, Inc.



F812-IO

## LINEAGE™

Simple, clean, architectural lines have been utilized to define the Lineage™.

### FEATURES

- 14° Blade Pitch • 5-Blades 54" Sweep • 6" Downrod
- Full Function Wall Control System Independent Up/Downlight
- Integrated Uplight Uses 6-15W Candelabra Bulbs (Included)
- Integrated Downlight Uses 2-60W Candelabra Bulbs (Included)
- Complements Lighting Available Through Minka-Lavery®

U.S. Patent(s): D528,652; D531,298; D532,098; D533,292; D535,012; D563,540

### ENERGY INFORMATION (Excludes Lights)

- Airflow CFM: 6,534 • Electricity Used Watts: 100 • Airflow Efficiency CFM/Watts: 65.34

**F812-IO** • Iron Oxide Finish • Dark Walnut Blades • Venetian Scavo Glass



F705-STW



**CM7038-STW 38"**  
Fits Napoli™ and Napoli™ II

## NAPOLI™ 56"

### FEATURES

- 14° Blade Pitch • 5-Blades 56" Sweep • 12" Downrod • Full Function Wall Control System
- Integrated Halogen Light Uses 2-50W Mini-Can Halogen Bulbs (Included)

U.S. Patent(s): D513,532; D514,685; D514,690; D516,702; D521,627; D522,122

### ENERGY INFORMATION (Excludes Lights)

- Airflow CFM: 6,765 • Electricity Used Watts: 93 • Airflow Efficiency CFM/Watts: 72

**F705-STW** • Sterling Walnut™ Finish • Sterling Walnut™ Shaded Blades • Aged Champagne Glass  
**CM7038-STW 38"** • Sterling Walnut™ Finish • Matching Ceiling Medallion for F705/F715 • © 2005 Minka Lighting, Inc.



F715-TSP



F715-STW



**CM7022-TSP 22"**  
**CM7022-STW 22"**  
*Fits Napoli™ and Napoli™ II*

## NAPOLI™ II 68"

### FEATURES

- 14° Blade Pitch • 5-Blades 68" Sweep • 12" Downrod • Full Function Wall Control System
- Integrated Halogen Light Uses 2-50W Mini-Can Halogen Bulbs (Included)

U.S. Patent(s): D513,532; D514,685; D514,690; D516,702; D521,627; D522,122

### ENERGY INFORMATION (Excludes Lights)

- Airflow CFM: 7,581 • Electricity Used Watts: 104 • Airflow Efficiency CFM/Watts: 72.84

**F715-TSP** • Tuscan Patina™ Finish • Tuscan Patina™ Shaded Blades • Aged Champagne Glass

**F715-STW** • Sterling Walnut™ Finish • Sterling Walnut™ Shaded Blades • Aged Champagne Glass

**CM7022-TSP 22"** • Tuscan Patina™ Finish • Matching Ceiling Medallion for F705/F715 • © 2005 Minka Lighting, Inc.

**CM7022-STW 22"** • Sterling Walnut™ Finish • Matching Ceiling Medallion for F705/F715 • © 2005 Minka Lighting, Inc.



F759-PBL

## CLASSICA GALLERY EDITION

Old world hand-painted finishes accentuate the hand-carved details to create a traditional European style fan.

### FEATURES

- 14° Blade Pitch • 5-Blades 54" Sweep • 6" Downrod
  - Integrated 3-Light Kit Uses 3-60W Candelabra Bulbs (Included) • Hand Held Remote Control System
- © 2009 Minka Lighting, Inc.

### ENERGY INFORMATION (Excludes Lights)

- Airflow CFM: 6,313 • Electricity Used Watts: 71.6 • Airflow Efficiency CFM/Watts: 88.17

**F759-PBL Gallery Edition** • Provencal Blanc Finish • Provencal Blanc Blades • Etched Glass



F759-PBL Gallery Edition



**F659-DRF**

**FEATURES**

- 14° Blade Pitch • 5-Blades 54" Sweep • 6" Downrod • 3-Speed Pull Chain
- Universal Light Kit Adaptable (Sold Separately. Page(s): 267)
- Custom Light Kit K9659 Available (Sold Separately. Page(s): 273)

© 2009 Minka Lighting, Inc.

**ENERGY INFORMATION** (Excludes Lights)

- Airflow CFM: 6,313 • Electricity Used Watts: 71.6 • Airflow Efficiency CFM/Watts: 88.17

**F659-DRF** • Driftwood Finish • Driftwood Blades



# CLASSICA

Old world hand-painted finishes accentuate the hand-carved details to create a traditional European style fan.



**F659-PBL**

## CLASSICA

Old world hand-painted finishes accentuate the hand-carved details to create a traditional European style fan.

### FEATURES

- 14° Blade Pitch • 5-Blades 54" Sweep • 6" Downrod • 3-Speed Pull Chain
- Universal Light Kit Adaptable (Sold Separately. Page(s): 267)
- Custom Light Kit K9659 Available (Sold Separately. Page(s): 273)

© 2009 Minka Lighting, Inc.

### ENERGY INFORMATION (Excludes Lights)

- Airflow CFM: 6,313 • Electricity Used Watts: 71.6 • Airflow Efficiency CFM/Watts: 88.17

**F659-PBL** • Provencal Blanc Finish • Provencal Blanc Blades

**F659-BCW** • Belcaro Walnut™ Finish • Dark Walnut Blades

**F659-FB** • French Beige Finish • Medium Maple Blades

**F659-PI** • Patina Iron Finish • Dark Walnut Blades

**F659-DRF** • Driftwood Finish • Driftwood Blades

# CLASSICA



F659-BCW



F659-FB



F659-PI



F659 Fans Only



F702-BCW



F702-VB

## VOLTERRA™

Volterra™ is a neo-classical inspiration, incorporating an uplight with an integrated halogen downlight.

### FEATURES

- 14° Blade Pitch • 5-Blades 52" Sweep • 6" Downrod
- Wall Control System Independent Up/Downlight
- Integrated Uplight Uses 6-15W Candelabra Bulbs (Included)
- Integrated Halogen Downlight Uses 2-50W Mini-Can Halogen Bulbs (Included)

© 2002 Minka Lighting, Inc.

### ENERGY INFORMATION (Excludes Lights)

- Airflow CFM: 5,425 • Electricity Used Watts: 67 • Airflow Efficiency CFM/Watts: 80.97

**F702-BCW** • Belcaro Walnut™ Finish • Natural Walnut Blades • Aged Champagne Glass  
**F702-VB** • Volterra Bronze™ Finish • Natural Walnut Blades • French Scavo Glass



F544-BCW



F544-GBZ

## CALAIS™

Elegance, style and performance for low ceiling applications, this fan has less than an 11-inch drop from ceiling to cap.

### FEATURES

- 14° Blade Pitch • 5-Blades 52" Sweep
- Flush Mount - Ideal for Low Ceilings Less than 11" Drop from Ceiling
- Hand Held Remote Control System
- Integrated Light Uses 2-60W Candelabra Bulbs (Included)

U.S. Patent(s): D526,714; D527,094; D530,415; D532,896; D536,777

### ENERGY INFORMATION (Excludes Lights)

- Airflow CFM: 6,050 • Electricity Used Watts: 79.8 • Airflow Efficiency CFM/Watts: 75.81

**F544-BCW** • Belcaro Walnut™ Finish • Dark Walnut Blades • Aged Champagne Glass  
**F544-GBZ** • Golden Bronze Finish • Dark Walnut Blades • Excavation Glass

# CRISTAFANO™



**F900-BCW**

*Shown with Optional GC900 SET*  
**MADE WITH SPECTRA® CRYSTAL**  
GC900 Set only fits with 16" Downrod





F900-BCW

**FEATURES**

- 14° Blade Pitch • 5-Blades 68" Sweep • 3½" and 16" Downrod
- Full Function Wall Control System with Independent Up/Downlight Control Feature
- Precision Machine Cut and Polished Lead-Free SPECTRA® CRYSTAL
- Integrated Uplight Uses 5-15W Candelabra Bulbs (Included)
- Integrated Halogen Downlight Uses 2-50W Mini-Can Halogen Bulbs (Included)

© 2005 Minka Lighting, Inc.

**ENERGY INFORMATION** (Excludes Lights)

- Airflow CFM: 6,022 • Electricity Used Watts: 95 • Airflow Efficiency CFM/Watts: 63.39

**F900-BCW** • Belcaro Walnut™ Finish • Dark Walnut Blades • Etched Cut Glass









**F307-MBK**  
*Oscillating Fan*

**F307-BN**  
*See Opposite Page*

## ANYWHERE

The first wall mount fan in the industry to be wet-rated brings a contemporary look and feel to any indoor or outdoor environment. ANYWHERE can be mounted to a standard electrical box or plugged in to an outlet. ANYWHERE is designed to conform to any décor and to any climate. Oscillating cool comfort where a ceiling fan may not be an option.

### FEATURES

- 3-Blade Turbofan 15" Diameter • 3 Speeds: 491, 650 and 985 R.P.M. • Oscillates 45° Side to Side
- Manual Tilt • 118" Heavy Duty Cord Length • 3 Speed Pull Chain
- Convertible to hardware or wall plug • Steel Construction • One Year Limited Warranty
- Indoor/Outdoor Use - UL Listed for Wet Locations

U.S. Patent(s): Pending

- F307-BN** • Brushed Nickel Finish • Silver Blades
- F307-MBK** • Matte Black Finish • Matte Black Blades





**F886-84-BNW**

## XTREME H<sub>2</sub>O 84"

An outdoor version of one of our most popular large fan introductions, this industrial sized fan lends itself to any setting. Xtreme H<sub>2</sub>O's clean, sleek, contemporary design, complete with a DC motor and a choice of sizes, makes it perfect for large areas indoor or outdoor.

### FEATURES

- 4° Blade Pitch • 8-Blades 84" Sweep • DC 123 x 30mm Motor • 6" Downrod
- Aluminum Blades • Install with Blades at least 10' above the Floor
- Special Hand Held Remote Control System Included - RC400
- Custom 20W LED Light Kit K9886L Available (Sold Separately. Page(s): 275)
- Indoor/Outdoor Use - UL Listed for Wet Locations

U.S. Patent(s): Pending

### ENERGY INFORMATION\*\* (Excludes Lights)

- Airflow CFM: 8,778 • Electricity Used Watts: 27.6 • Airflow Efficiency CFM/Watts: 318.04

**F886-84-BNW** • Brushed Nickel Wet Finish • Silver Blades

**F886-84-SI** • Smoked Iron Finish • Smoked Iron Blades

**F886-84-ORB** • Oil Rubbed Bronze Finish • Oil Rubbed Bronze Blades

# XTREME H<sub>2</sub>O



**F886-84-SI**  
*Shown with optional  
K9886L-SI LED light kit*



**F886-84-ORB**





F886-65-BNW

## XTREME H<sub>2</sub>O 65"

An outdoor version of one of our most popular large fan introductions, this industrial sized fan lends itself to any setting. Xtreme H<sub>2</sub>O's clean, sleek, contemporary design, complete with a DC motor and a choice of sizes, makes it perfect for large areas indoor or outdoor.

### FEATURES

- 4° Blade Pitch • 8-Blades 65" Sweep • DC 123 x 30mm Motor • 6" Downrod
- Aluminum Blades • Install with Blades at least 10' above the Floor
- Special Hand Held Remote Control System Included - RC400
- Custom 20W LED Light Kit K9886L Available (Sold Separately. Page(s): 275)
- Indoor/Outdoor Use - UL Listed for Wet Locations

U.S. Patent(s): Pending

### ENERGY INFORMATION\*\* (Excludes Lights)

- Airflow CFM: 8,778 • Electricity Used Watts: 27.6 • Airflow Efficiency CFM/Watts: 318.04

- F886-65-BNW** • Brushed Nickel Wet Finish • Silver Blades
- F886-65-ORB** • Oil Rubbed Bronze Finish • Oil Rubbed Bronze Blades
- F886-65-WHF** • Flat White Finish • Flat White Blades

# XTREME H<sub>2</sub>O



**F886-65-ORB**  
Shown with optional  
K9886L-ORB LED light kit



**F886-65-WHF**  
Shown with optional  
K9886L-WHF LED light kit





**F402-BNW**

**F402-ORB**  
See Opposite Page

## GYRO™ WET

Capturing the design elements of the original Gyro™, the Gyro™ Wet provides unsurpassed performance and comfort levels in the toughest environments. Rotating 360° and controlled by a wall control system, it offers wonderful cooling in any area and the option to stop and redirect air for maximum benefit.

### FEATURES

- High Performance Twin Turbofans Total Sweep 42" • 20° Blade Pitch
- Complete Assembly Rotates 360° at 3 R.P.M. • 720 - 1,350 R.P.M. Fan Speeds
- Turbofan Heads Adjustable Up and Down • Galvanized Steel 6" Downrod
- Full Function Wall Control System Incorporating Fully Independent Fan Head Speeds and Lighting Fixture
- Integrated Halogen Light Uses 1-100W Mini-Can Halogen Bulb (Included)
- Cap for Non-Light Use (Included) • Indoor/Outdoor Use UL Listed for Wet Locations

U.S. Patent(s): D478,975; D489,443; D489,809; D490,146; 6,832,902; 7,183,680; 7,229,255

### ENERGY INFORMATION (Excludes Lights)

- Airflow CFM: 5,050 • Electricity Used Watts: 102 • Airflow Efficiency CFM/Watts: 49.51

**F402-ORB** • Oil Rubbed Bronze Finish • Oil Rubbed Bronze Blades • Etched Opal School House Globe Glass  
**F402-BNW** • Brushed Nickel Wet Finish • Silver Blades • Etched Opal Glass





F402-ORB



**F787-ORB**

## SIMPLE

So simple! We gave this wonderful design a name that best denotes it's spirit! Incredibly delicate and nearly invisible. This design best displays the advancement in technology with indoor/outdoor use, DC motor, optional LED\* light kit and a hand held remote.

### FEATURES

- 14° Blade Pitch • 3-Blades 52" Sweep • DC 123 x 30mm Motor • 6" Downrod
- Special Hand Held Remote Control System Included - RC400
- Custom 15W LED Light Kit K9787L Available (Sold Separately. Page(s): 275)
- Indoor/Outdoor Use ETL Listed for Wet Locations

### ENERGY INFORMATION (Excludes Lights)

- Airflow CFM: 7,051 • Electricity Used Watts: 33.1 • Airflow Efficiency CFM/Watts: 213

**F787-ORB** • Oil Rubbed Bronze Finish • Medium Maple Blades

**F787-SL** • Silver Finish • Silver Blades

**F787-WHF** • Flat White Finish • Flat White Blades

# SIMPLE



**F787-SL**



**F787-WHF**  
Shown with optional  
K9787L-WHF LED Light Kit

*Available Optional LED Light Kit*



K9787L-SL



K9787L-ORB

**DC** MOTOR



# GROTON



**F681-SDBK/WS**



**F681-BNW**



**F681-WA/PW**



**F681-PN**  
*(Finish For Indoor Use Only)*





**F681-ORB**

# GROTON

Inspired by the clear Fresnel lens used in lighthouses along the coast of Connecticut, we are introducing our Groton collection. Classic design combined with nautical spirit in various finishes. All which will suit both indoor and outdoor locations, as this fan has a UL wet rating.

## FEATURES

- 12° Blade Pitch • 5-Blades 56" Sweep • 10" Downrod
- Full Function Hand Held Remote Control System
- Integrated Halogen Light Uses 2-50W Mini-Can Halogen Bulbs (Included)
- Indoor/Outdoor Use UL Listed for Wet Locations

U.S. Patent(s): Pending

## ENERGY INFORMATION (Excludes Lights)

- Airflow CFM: 6,392 • Electricity Used Watts: 64.8 • Airflow Efficiency CFM/Watts: 98.64

**F681-ORB** • Oil Rubbed Bronze Finish • Dark Pine Blades • Clear Fresnel Lens

**F681-SDBK/WS** • Sand Black / Weathered Steel Finish • Charcoal Driftwood Blades • Clear Fresnel Lens

**F681-BNW** • Brushed Nickel Wet Finish • Silver Blades • Clear Fresnel Lens

**F681-WA/PW** • Weathered Aluminum / Pewter Finish • Dark Pine Blades • Clear Fresnel Lens

**F681-PN** • Polished Nickel Finish • Silver Blades • Clear Fresnel Lens



**F624-ORB**

## ROTO XL

Roto XL features a sleek and contemporary design with a classic industrial look. Well edited; an impeccably executed design features a slight "fold" construction along the length of the blades to increase the flow of air. A perfect marriage of form and function. Roto XL features a full 62-inch spread combined with a wet location specification use for indoor or outdoors.

### FEATURES

- 20° Blade Pitch • 3-Blades 62" Sweep • 6" Downrod • Aluminum Construction
  - Convertible to Electronic Control System • Indoor/Outdoor Use - ETL Listed for Wet Locations
- U.S. Patent(s): D750,221 Additional U.S. Patent(s) Pending

### ENERGY INFORMATION (Excludes Lights)

- Airflow CFM: 7,567 • Electricity Used Watts: 70.69 • Airflow Efficiency CFM/Watts: 107.04

**F624-ORB** • Oil Rubbed Bronze Finish • Oil Rubbed Bronze Blades

**F624-ABD** • Brushed Aluminum Finish • Silver Blades

**F624-WHF** • Flat White Finish • Flat White Blades

# ROTO XL



**F624-ABD**



**F624-WHF**





F477-ORB

## CONCEPT™ I WET 58"

UL listed for use indoors and outdoors, furthering the versatility and timeless perfection that is the Concept™ I series. Concept™ I Wet is constructed of marine grade stainless steel to ensure long lasting appearance and function in the toughest environments.

### FEATURES

- 14° Blade Pitch • 3-Blades 58" Sweep • Marine Grade Stainless Steel Construction
- Stainless Steel 6" Downrod • Full Function Wall Control System
- Integrated Halogen Light Uses 1-100W Mini-Can Halogen Bulb (Included)
- Indoor/Outdoor Use UL Listed for Wet Locations • Cap for Non-Light Use (Included)

U.S. Patent(s): D475,782; D476,408; D478,654; D478,980; 7,008,192

### ENERGY INFORMATION (Excludes Lights)

- Airflow CFM: 7,026 • Electricity Used Watts: 65.4 • Airflow Efficiency CFM/Watts: 107.43

**F477-ORB** • Oil Rubbed Bronze Finish • Oil Rubbed Bronze Blades • Pietra Glass

**F477-BNW** • Brushed Nickel Wet Finish • Silver Blades • White Opal Glass

**F477-WH** • White Finish • White Blades • White Opal Glass

# CONCEPT™ I WET 58"



**F477-BNW**  
*Shown with Cap for Non-Light Use*



**F477-WH**  
*Shown with Cap for Non-Light Use*





F577-BNW

## CONCEPT™ I WET 52"

The Concept™ I ceiling fan collection is the most successful series in the history of Minka-Aire®. It is only natural that we would produce a new version that is UL listed for use indoors and outdoors, furthering the versatility and timeless perfection that is the Concept™ I series.

### FEATURES

- 14° Blade Pitch • 3-Blades 52" Sweep • Galvanized Steel 6" Downrod
- Construction Grade Polymer • Full Function Wall Control System
- Integrated Halogen Light Uses 1-100W Mini-Can Halogen Bulb (Included)
- Indoor/Outdoor Use UL Listed for Wet Locations • Cap for Non-Light Use (Included)

U.S. Patent(s): D475,782; D476,408; D478,654; D478,980; 7,008,192

### ENERGY INFORMATION (Excludes Lights)

- Airflow CFM: 5,991 • Electricity Used Watts: 51.2 • Airflow Efficiency CFM/Watts: 117.01

**F577-BNW** • Brushed Nickel Wet Finish • Silver Blades • White Opal Glass  
**F476-ORB** • Oil Rubbed Bronze Finish • Taupe Blades • Pietra Glass  
**F476-WH** • White Finish • White Blades • White Opal Glass

# CONCEPT™ | WET 52"



**F476-ORB**



**F476-WH**  
*Shown with Cap for Non-Light Use*





F474-ORB



F474-WH  
Shown with Cap for Non-Light Use

F574-BNW  
See Opposite Page

## CONCEPT™ II WET 52"

As the name implies, the Concept™ II Wet ceiling fan is “a taste of things to come.” Simple in style, yet ingenious by design and UL Listed for wet locations.

**FEATURES**

- 14° Blade Pitch • 3-Concave Blades 52" Sweep
  - Flush Mount - Ideal for Low Ceilings Total Hanging Depth 12" Drop from Ceiling
  - Construction Grade Polymer • Full Function Wall Control System
  - Integrated Halogen Light Uses 1-100W Mini-Can Halogen Bulb (Included)
  - Cap for Non-Light Use (Included)
  - Indoor/Outdoor Use UL Listed for Wet Locations (Will Not Pendulum In Windy Conditions)
- U.S. Patent(s): D478,654; D478,974; D478,980; 7,008,192

**ENERGY INFORMATION** (Excludes Lights)

- Airflow CFM: 6,053 • Electricity Used Watts: 51.3 • Airflow Efficiency CFM/Watts: 117.99

- F574-BNW** • Brushed Nickel Wet Finish • Silver Blades • White Opal Glass
- F474-ORB** • Oil Rubbed Bronze Finish • Taupe Blades • Pietra Glass
- F474-WH** • White Finish • White Blades • White Opal Glass



F574-BNW



CONCEPT™ II WET 52" 183



**F594-ORB**

## TRADITIONAL CONCEPT™ 52"

A variation on our best selling contemporary Concept™ II fan, this fan provides the same superb styling for your more traditional indoor and outdoor settings.

### FEATURES

- 14° Blade Pitch • 3-Blades 52" Sweep
- Flush Mount - Ideal for Low Ceilings Total Hanging Depth 11" Drop from Ceiling
- Full Function Wall Control System
- Integrated Halogen Light Uses 1-100W Mini-Can Halogen Bulb (Included)
- Indoor/Outdoor Use UL Listed for Wet Locations • Cap for Non-Light Use (Included)

### ENERGY INFORMATION (Excludes Lights)

- Airflow CFM: 6,565 • Electricity Used Watts: 61 • Airflow Efficiency CFM/Watts: 108.52

**F594-ORB** • Oil Rubbed Bronze Finish • Medium Maple Blades • Tinted Opal Glass

**F594-PW** • Pewter Finish • Dark Maple Blades • Opal Glass

**F594-WH** • White Finish • White Blades • Opal Glass

# TRADITIONAL CONCEPT™ 52"



F594-PW



F594-WH





F593-PW

## TRADITIONAL CONCEPT™ 44"

A variation on our best selling contemporary Concept™ II fan, this fan provides the same superb styling for your more transitional indoor and outdoor settings.

### FEATURES

- 14° Blade Pitch • 3-Blades 44" Sweep
- Flush Mount - Ideal for Low Ceilings Total Hanging Depth 11" Drop from Ceiling
- Full Function Wall Control System
- Integrated Halogen Light Uses 1-100W Mini-Can Halogen Bulb (Included)
- Indoor/Outdoor Use UL Listed for Wet Locations • Cap for Non-Light Use (Included)

### ENERGY INFORMATION (Excludes Lights)

- Airflow CFM: 4,940 • Electricity Used Watts: 49 • Airflow Efficiency CFM/Watts: 100

- F593-PW** • Pewter Finish • Dark Maple Blades • Opal Glass  
**F593-ORB** • Oil Rubbed Bronze Finish • Medium Maple Blades • Tinted Opal Glass  
**F593-WH** • White Finish • White Blades • Opal Glass

# TRADITIONAL CONCEPT™ 44"



F593-ORB



**F593-WH**

*Shown with Cap for Non-Light Use*



# JAVA LED

with LED Light



F753L-BNW



F753L-WHF





**F753L-KA**

## JAVA LED

with LED Light

Minka-Aire's "everywhere" fan with a unique contemporary twist that is suitable for all indoor or outdoor environments.

The Java LED features an integrated 17 watt LED\* light.

### FEATURES

- 15° Blade Pitch • 3-Blades 54" Sweep • 6" Downrod • Hand Held Remote Control System
- Integrated LED Light Uses 17W LED (Included) 3 Year Warranty • 1,350 Lumens • 3,000K • CRI 80
- Indoor/Outdoor Use - UL Listed for Wet Locations

### ENERGY INFORMATION (Excludes Lights)

- Airflow CFM: 5,682 • Electricity Used Watts: 47 • Airflow Efficiency CFM/Watts: 121

**F753L-KA** • Kocoba Finish • Kocoba Blades • Etched Opal Glass

**F753L-BNW** • Brushed Nickel Wet Finish • Silver Blades • Etched Opal Glass

**F753L-WHF** • Flat White Finish • Flat White Blades • Etched Opal Glass



**F753-KA**

## JAVA

Minka-Aire's "everywhere" fan with a unique contemporary twist that is suitable for all environments.

### **FEATURES**

- 14° Blade Pitch • 3-Blades 54" Sweep • 6" Downrod • Hand Held Remote Control System
- Indoor/Outdoor Use - UL Listed for Wet Locations

### **ENERGY INFORMATION** (Excludes Lights)

- Airflow CFM: 5,682 • Electricity Used Watts: 47 • Airflow Efficiency CFM/Watts: 121

- F753-KA** • Kocoa Finish • Kocoa Blades
- F753-WHF** • Flat White Finish • Flat White Blades
- F753-BNW** • Brushed Nickel Wet Finish • Silver Blades

# JAVA



F753-WHF



F753-BNW





**F523-ABD**

*Shown with Cap for Non-Light Use*

# ALUMA WET

Aluma Wet is our answer to the fan that goes anywhere and has everything. For use indoors and outdoors, Aluma Wet is UL listed for use in wet locations. Produced from weather resistant materials, the Aluma Wet provides air circulation for every location including patio, porch and pergola.

**FEATURES**

- 12° Blade Pitch • 4-Blades 52" Sweep • 6" Downrod • All Aluminum Construction
- Hand Held Remote Control System
- Integrated Halogen Light Uses 1-100W Mini-Can Halogen Bulb (Included)
- Indoor/Outdoor Use UL Listed for Wet Locations • Cap for Non-Light Use (Included)

**ENERGY INFORMATION** (Excludes Lights)

- Airflow CFM: 4,834 • Electricity Used Watts: 51.5 • Airflow Efficiency CFM/Watts: 93.88

- F523-ABD** • Brushed Aluminum Finish • Silver Blades • Etched Opal Glass
- F523-WHF** • Flat White Finish • Flat White Blades • Etched Opal Glass
- F523-ORB** • Oil Rubbed Bronze Finish • Oil Rubbed Bronze Blades • Tinted Opal Glass

# ALUMA WET



F523-WHF



F523-ORB





**F734-ORB**

# STRATA

The Strata with its Smoked Iron or Galvanized finishes adds a rustic yet contemporary style to your home.

## FEATURES

- 12° Blade Pitch • 4-Blades 52" Sweep
- Galvanized Steel 6" Downrod (Uses  $\frac{3}{4}$ " I.D. DR5 Series Downrod)
- Hand Held Remote Control System • Integrated Light Uses 1-75W Mini-Can Halogen Bulb (Included)
- Indoor/Outdoor Use UL Listed for Wet Locations • Cap for Non-Light Use (Included)

## ENERGY INFORMATION (Excludes Lights)

- Airflow CFM: 5,098 • Electricity Used Watts: 49 • Airflow Efficiency CFM/Watts: 104.4

**F734-ORB** • Oil Rubbed Bronze Finish • Oil Rubbed Bronze Blades • Tinted Opal Glass

**F734-GL** • Galvanized Finish • Silver Blades • Etched Opal Glass

**F734-SI** • Smoked Iron Finish • Smoked Iron Blades • Etched Opal Glass

# STRATA



**F734-GL**  
*Shown with Cap for Non-Light Use*



**F734-SI**





**F683L-BNW**

## SHADE

with LED Light

Illumination even in the harshest of environments. SHADE provides unmatched performance and comfort in the toughest conditions. Incorporating a DC motor for high efficiency with an integrated 15 watt LED light and a UL wet rating, SHADE meets both your indoor and outdoor location requirements.

### FEATURES

- 14° Blade Pitch • 4-Blades 56" Sweep • 6" Downrod • DC 168 x 12mm Motor
- Hand Held Remote Control System - RC400
- Integrated LED Light Uses 15W LED (Included) 3 Year Warranty • 1,800 Lumens • 3,000K • CRI 80
- Indoor/Outdoor Use - UL Listed for Wet Locations

U.S. Patent(s): Pending

### ENERGY INFORMATION\*\* (Excludes Lights)

- Airflow CFM: 6,000 • Electricity Used Watts: 29 • Airflow Efficiency CFM/Watts: 206

**F683L-BNW** • Brushed Nickel Wet Finish • Silver Blades • Clear Fresnel Glass

**F683L-GI** • Grey Iron Finish • Matte Black Blades • Clear Fresnel Glass

**F683L-HBZ** • Heirloom Bronze Finish • Charcoal Blades • Clear Fresnel Glass

# SHADE

with LED Light



F683L-GI



F683L-HBZ

### Optional Shade



Optional  
Green Shade  
FS683L-GRN



Optional  
Red Shade  
FS683L-RD



Optional  
White Shade  
FS683L-WH



Optional  
Tarnished Copper Shade  
FS683L-TRN

LED

DC MOTOR



minkaAire®

# RAINMAN™



F582-ORB



F582-BNW



F582-GL





F582-SI

## RAINMAN™

Reminiscent of lighting often found along shoreline walkways, the Rainman™, as the name suggests, is an excellent choice for exterior as well as interior use.

### FEATURES

- 14° Blade Pitch • 5-Blades 54" Sweep • Galvanized Steel 6" Downrod
- Stainless Steel Hardware and All Weather Blades • Wall Control System
- Integrated Halogen Caged Light Uses 1-100W Mini-Can Halogen Bulb (Included)
- Indoor/Outdoor Use UL Listed for Wet Locations

### ENERGY INFORMATION (Excludes Lights)

- Airflow CFM: 5,508 • Electricity Used Watts: 58 • Airflow Efficiency CFM/Watts: 94.96

- F582-SI** • Smoked Iron Finish • Smoked Iron Blades • Acid Etched Glass
- F582-ORB** • Oil Rubbed Bronze Finish • Taupe Blades • Vintage Amber Glass
- F582-BNW** • Brushed Nickel Wet Finish • Silver Blades • Acid Etched Glass
- F582-GL** • Galvanized Finish • Silver Blades • Acid Etched Glass



**F888-BNW**

## SLIPSTREAM

Sleek industrial styling destines this 8-bladed wonder to make a cool statement in any indoor or outdoor setting.

### FEATURES

- 14° Blade Pitch • 8-Concave Blades 65" Sweep • DC 165 x 25mm Motor
- Galvanized Steel 6" Downrod • Stainless Steel Hardware and All Weather Blades
- Special Hand Held Remote Control System Included - RC400
- Integrated Light Uses 1-18W GU24 Non-Dimmable Squat CFL (Included)
- Cap for Non-Light Use (Included) • Indoor/Outdoor Use UL Listed for Wet Locations

U.S. Patent(s): D715,917

### ENERGY INFORMATION (Excludes Lights)

- Airflow CFM: 8,778 • Electricity Used Watts: 27.6 • Airflow Efficiency CFM/Watts: 318.04

**F888-BNW** • Brushed Nickel Wet Finish • Silver Blades • Etched Opal Glass

**F888-WHF** • Flat White Finish • Flat White Blades • Etched Opal Glass

**F888-DK** • Distressed Koa Finish • Distressed Koa Blades • Tinted Opal Glass

**F888-ORB** • Oil Rubbed Bronze Finish • Oil Rubbed Bronze Blades • Tinted Opal Glass

# SLIPSTREAM



**F888-WHF**



**F888-DK**



**F888-ORB**  
*Shown with Cap for Non-Light Use*

DC MOTOR



minkaAire®



F532-SI

## SUNSEEKER

The Sunseeker features a 60-inch sweep, stylish transitional design and superb value. These elements make it an ideal choice for enjoying hot summer days outdoors.

### FEATURES

- 14° Blade Pitch • 5-Blades 60" Sweep • Galvanized Steel 6" Downrod
- Stainless Steel Hardware and All Weather Blades • 3-Speed Pull Chain
- Indoor/Outdoor Use UL Listed for Wet Locations
- UL Wet Location Light Kits Available (Sold Separately. Page(s): 267)

### ENERGY INFORMATION (Excludes Lights)

- Airflow CFM: 6,783 • Electricity Used Watts: 65 • Airflow Efficiency CFM/Watts: 104.19

**F532-SI** • Smoked Iron Finish • Smoked Iron Blades

**F532-BNW** • Brushed Nickel Wet Finish • Silver Blades

**F532-DRF** • Driftwood Finish • Driftwood Blades

**F532-ORB** • Oil Rubbed Bronze Finish • Oil Rubbed Bronze Blades

**F532-BWH** • Bone White Finish • Bone White Blades

# SUNSEEKER



F532-BNW



F532-DRF



F532-ORB



F532-BWH





F589-ORB

## SUNDOWNER®

Highly recommended for the most challenging environments, the Sundowner® combines superior performance with weatherproof components designed to withstand all outdoor conditions.

### FEATURES

- 16° Blade Pitch • 5-Blades 54" Sweep • Galvanized Steel 6" Downrod
- Stainless Steel Hardware and All Weather Blades • 3-Speed Pull Chain
- Poly Molded and ABS Components • Indoor/Outdoor Use UL Listed for Wet Locations
- UL Wet Location Light Kits Available (Sold Separately. Page(s): 267)

Accessory Blades Available. See Page(s): 288

### ENERGY INFORMATION (Excludes Lights)

- Airflow CFM: 6,523 • Electricity Used Watts: 79 • Airflow Efficiency CFM/Watts: 82

- F589-ORB** • Oil Rubbed Bronze Finish • Dark Maple Blades
- F589-DRF** • Driftwood Finish • Driftwood Blades
- F589-MW** • Mossoro Walnut™ Finish • Mossoro Walnut™ Blades
- F589-BWH** • Bone White Finish • Bone White Blades

# SUNDOWNER®



F589-DRF



F589-MW



F589-BWH





F589-HT

## SUNDOWNER®

- F589-HT** • Heritage™ Finish • Black Blades
- F589-VRT** • Vintage Rust™ Finish • Dark Maple Blades
- F589-BI/AI** • Black Iron with Aged Iron Accents Finish • Black Iron Blades
- F589-WH** • White Finish • White Blades

# SUNDOWNER®



F589-VRT



F589-BI/AI



F589-WH





**F571-DRF 52"**

## SUNDANCE™

Perfect for the porch, patio, gazebo or courtyard, the Sundance™ was designed to withstand all of the elements.

### FEATURES

- 12° Blade Pitch • 5-Blades 52" or 42" Sweep • Galvanized Steel 6" Downrod
- Stainless Steel Hardware and All Weather Blades • 3-Speed Pull Chain
- Indoor/Outdoor Use UL Listed for Wet Locations
- UL Wet Location Light Kits Available (Sold Separately. Page(s): 267)

### F571 ENERGY INFORMATION (Excludes Lights)

- Airflow CFM: 5,596 • Electricity Used Watts: 63 • Airflow Efficiency CFM/Watts: 88.4

### F572 ENERGY INFORMATION (Excludes Lights)

- Airflow CFM: 3,428 • Electricity Used Watts: 52 • Airflow Efficiency CFM/Watts: 65.64

**F571-DRF 52"** • Driftwood Finish • Gray Blades

**F571-WH 52"** • White Finish • White Blades

**F571-ORB 52"** • Oil Rubbed Bronze Finish • Dark Oak Finish Blades

**F572-WH 42"** • White Finish • White Blades

**F572-ORB 42"** • Oil Rubbed Bronze Finish • Dark Oak Finish Blades

# SUNDANCE™



F571-WH 52"



F571-ORB 52"



F572-WH 42"



F572-ORB 42"





**F581-BG**

## GAUGUIN™

Tropical style influences the Gauguin™ by incorporating a remarkable combination of performance and unique design elements.

### FEATURES

- 14° Blade Pitch • 4-Blades 52" Sweep
- Galvanized Steel 6" Downrod (Uses 3/4" I.D. DR5 Series Downrod)
- Stainless Steel Hardware and All Weather Blades • Full Function Wall Control System
- Integrated Halogen Light Uses 1-50W MR16 120V 2-Pin Halogen Bulb (Included)
- Custom Ceiling Adapter Kit A581 Available (Sold Separately. Page(s): 286)
- Indoor/Outdoor Use UL Listed for Wet Locations • Cap for Non-Light Use (Included)

U.S. Patent(s): D513,319; D514,691; D514,692; D516,703; D517,201; D519,199

### ENERGY INFORMATION (Excludes Lights)

- Airflow CFM: 4,834 • Electricity Used Watts: 52 • Airflow Efficiency CFM/Watts: 92.97

**F581-BG** • Bahama Beige™ Finish • Bahama Beige™ Blades • Etched Glass

**F581-WHF** • Flat White Finish • Flat White Blades • Etched Glass

**F581-ORB** • Oil Rubbed Bronze Finish • Bahama Beige™ Blades • Etched Glass



**F581-WHF**



**F581-ORB**



**F581-BG**

*Shown with Optional A581-BG Ceiling Adapter  
For Flush Mount Applications*





F580-VR/BB



F580-VR/BB  
*Shown with Cap for Non-Light Use*

## SHANGRI-LA®

Our wicker design, coupled with a Vintage Rust™ finish, replicates a highly popular tropical motif.

### FEATURES

- 14° Blade Pitch • 5-Blades 52" Sweep • Galvanized Steel 6" Downrod
- Stainless Steel Hardware and All Weather Blades • 3-Speed Pull Chain
- Snap Lock/Set Screw Blade Assembly System
- Integrated Halogen Caged Etched Glass Light Uses 1-100W Mini-Can Halogen Bulb (Included)
- Indoor/Outdoor Use UL Listed for Wet Location • Cap for Non-Light Use (Included)

U.S. Patent(s): D501,251; D501,922; D501,923; D502,770; D508,287; D514,215; D522,643; 7,008,192

### ENERGY INFORMATION (Excludes Lights)

- Airflow CFM: 5,375 • Electricity Used Watts: 79 • Airflow Efficiency CFM/Watts: 68.03

**F580-VR/BB** • Vintage Rust™ Finish • Bamboo All Weather Blades • Caged Etched Glass





F840-CF



F840-CF

*Shown with Cap for Non-Light Use*

## CRAFTSMAN™

Inspired by the Craftsman architecture of the early 1900s, this fan best defines the spirit of the era. It can be used in both interior and exterior applications.

### FEATURES

- 14° Blade Pitch • 5-Blades 52" Sweep • Galvanized Steel 6" Downrod
- Stainless Steel Hardware and All Weather Blades • Full Function Wall Control System
- Light Kit with Enclosed Glass Shades Uses 3-60W Candelabra Bulbs (Included)
- Indoor/Outdoor Use UL Listed for Wet Locations • Cap for Non-Light Use (Included)

U.S. Patent(s): D579,097; D579,098; D579,103; D581,512; D583,044

### ENERGY INFORMATION (Excludes Lights)

- Airflow CFM: 5,374 • Electricity Used Watts: 77.7 • Airflow Efficiency CFM/Watts: 69.16

**F840-CF** • Craftsman™ Finish • Craftsman™ Blades • Craftsman™ Glass







## VALUE COLLECTION

---

With the Minka-Aire® Value Collection, one need not sacrifice style and performance for affordability.

Choose from several finishes and light kit options to find the right Minka-Aire® ceiling fan with timeless style and design for the budget-conscious customer.



**F534L-ORB**

## LUN-AIRE

with LED Light

A versatile, all-in-one “everything” fan, Lun-Aire, with its five blades and three speeds, will be the hardest worker in the room. A simplistic, yet sophisticated design, combined with a cost efficient motor and inspired engineering for superior performance, Lun-Aire is destined to become the smartest, most dynamic orb for any room

### FEATURES

- 12° Blade Pitch • 5-Blades 54" Sweep • 6" Downrod • 3 Speed Pull Chain
  - Integrated LED Light Uses 17W LED (Included) 3 Year Warranty • 1,100 Lumens • 3,000K • CRI 80
- U.S. Patent(s): Pending

### ENERGY INFORMATION\*\* (Excludes Lights)

- Airflow CFM: 5,400 • Electricity Used Watts: 50 • Airflow Efficiency CFM/Watts: 108

**F534L-ORB** • Oil Rubbed Bronze Finish • Dark Pine Blades • Etched Opal Glass

**F534L-WH** • White Finish • White Blades • Etched Opal Glass

**F534L-BN** • Brushed Nickel Finish • Silver Blades • Etched Opal Glass

# LUN-AIRE

with LED Light



F534L-WH



F534L-BN

LED



F727-BN/MM





**F727-BN/SL**



**F727-ORB**



**F727-DK**

**F727-BN/MM**  
See Opposite Page

## RUDOLPH

Inspired by a contemporary architect of the 50's, this clean three blade design best exemplifies today's trend in home furnishings. Included is a wall control, cast blade holders and a 172 x 16mm motor for great air movement.

### FEATURES

- 14° Blade Pitch • 3-Blades 52" Sweep • 6" Downrod
- Convertible to Electronic Control System • Wall Control System - WC116 Included
- Universal Light Kit Adaptable (Sold Separately. Page(s): 267)

### ENERGY INFORMATION (Excludes Lights)

- Airflow CFM: 6,665 • Electricity Used Watts: 84.94 • Airflow Efficiency CFM/Watts: 78.47

**F727-BN/MM** • Brushed Nickel Finish • Medium Maple Blades

**F727-BN/SL** • Brushed Nickel Finish • Silver Blades

**F727-ORB** • Oil Rubbed Bronze Finish • Tobacco Blades

**F727-DK** • Distressed Koa Finish • Distressed Koa Blades



### F1000-BN

Shown with Dark Walnut Blades  
Reversible to Medium Maple Blades

## DYNO

with LED Light

An addition to our Value Collection, featuring performance and design features at an affordable price. For the first time in our Value offerings, we introduce a fan with an integrated LED\* light source. Generous in size, style, adaptability and function, Dyno becomes one of our core fan offerings.

### FEATURES

- 12° Blade Pitch • 5-Blades 52" Sweep • 6" Downrod
  - Integrated Light Uses 17W Dimmable LED (Included) 3 Year Warranty • 1,100 Lumens • 2,700K
  - CRI 80 • Hand Held Remote Control System • Replacement LED Assembly (Part #6F1000LK01)
- U.S. Patent(s): D762,836; D762,839; Additional U.S. Patent(s) Pending

### ENERGY INFORMATION (Excludes Lights)

- Airflow CFM: 5,295 • Electricity Used Watts: 68.93 • Airflow Efficiency CFM/Watts: 76.82

- F1000-BN** • Brushed Nickel Finish • Reversible Medium Maple / Dark Walnut Blades • Etched Lens
- F1000-ORB** • Oil Rubbed Bronze Finish • Reversible Medium Maple / Dark Walnut Blades • Etched Lens
- F1000-WH** • White Finish • White Blades • Etched Lens

**DYNO**  
with LED Light



**F1000-ORB**  
*Shown with Dark Walnut Blades  
Reversible to Medium Maple Blades*



**F1000-WH**



**F729-GM**

## STEAL

Inspired by the revolution that moved us from hand production methods to machines, and drove new manufacturing processes and iron production, Steal marks a major turning point in industrial style and design.

### FEATURES

- 5° Blade Pitch • 3-Blades 54" Sweep • 188 x 15mm Motor • 6" Downrod
- Install with Blades at least 10' above the Floor • 2-Wire Installation Wall Control Included - WC105
- Universal Light Kit Adaptable (Sold Separately. Page(s): 267)

### ENERGY INFORMATION\*\* (Excludes Lights)

- Airflow CFM: 5,816 • Electricity Used Watts: 51.6 • Airflow Efficiency CFM/Watts: 113

- F729-GM** • Gun Metal Finish • Gun Metal Blades
- F729-WHF** • Flat White Finish • Flat White Blades
- F729-BN** • Brushed Nickel Finish • Brushed Nickel Blades

STEAL



F729-WHF



F729-BN

# TRADITIONAL MOJO



**F622-BWH**



**F622-ORB**  
*Shown with Medium Maple Blades  
Reversible to Dark Walnut Blades*



**F622-ORB/TS**  
*Shown with Medium Maple Blades  
Reversible to Dark Walnut Blades*



**F622-PW**  
 Shown with Dark Walnut Blades  
 Reversible to Medium Maple Blades

## TRADITIONAL MOJO

The Traditional Mojo is the next generation of our highly successful Mojo series. Traditional accents integrate perfectly for your home.

### FEATURES

- 12° Blade Pitch • 5-Blades 52" Sweep • 6" Downrod • 3-Speed Pull Chain
- Low Profile Bowl Light Kit Uses 3-60W Candelabra Bulbs (Included)
- Cap for Non-Light Use (Included)
- Solid Cap and Finial Adaptation for Remote Control Use (Included)

### ENERGY INFORMATION (Excludes Lights)

- Airflow CFM: 5,699 • Electricity Used Watts: 66.1 • Airflow Efficiency CFM/Watts: 86.22

**F622-PW** • Pewter Finish • Reversible Medium Maple / Dark Walnut Blades • Etched White Glass

**F622-BWH** • Bone White Finish • Bone White Blades • Bone White Glass

**F622-ORB** • Oil Rubbed Bronze Finish • Reversible Medium Maple / Dark Walnut Blades • Etched White Glass

**F622-ORB/TS** • Oil Rubbed Bronze Finish • Reversible Medium Maple / Dark Walnut Blades • Tea Stain Glass



**F522-ORB/TS**

*Shown with Medium Maple Blades  
Reversible to Dark Walnut Blades*

## Mojo

**FEATURES**

- 12° Blade Pitch • 5-Blades 52" Sweep • 6" Downrod • 3-Speed Pull Chain
- Low Profile Light Kit Uses 3-60W Candelabra Bulbs (Included) • Warp Resistant Plywood Blades
- Cap for Non-Light Use (Included)
- Solid Cap and Finial Adaptation Kit for Remote Control Use (Included)

**ENERGY INFORMATION** (Excludes Lights)

- Airflow CFM: 5,295 • Electricity Used Watts: 65.7 • Airflow Efficiency CFM/Watts: 81

**F522-ORB/TS** • Oil Rubbed Bronze Finish • Reversible Medium Maple / Dark Walnut Blades • Tea Stain Glass

**F522-WH** • White Finish • White Blades • Frosted White Glass

**F522-BWH** • Bone White Finish • Bone White Blades • Frosted White Glass

**F522-ORB** • Oil Rubbed Bronze Finish • Reversible Medium Maple / Dark Walnut Blades • Frosted White Glass

**F522-BN** • Brushed Nickel Finish • Reversible Medium Maple / Dark Walnut Blades • Frosted White Glass



**F522-WH**



**F522-BWH**



**F522-ORB**

*Shown with Medium Maple Blades  
Reversible to Dark Walnut Blades*



**F522-BN**

*Shown with Medium Maple Blades  
Reversible to Dark Walnut Blades*

# Mojo II



**F533-BN**  
*Shown with Dark Walnut Blades  
Reversible to Medium Maple Blades*



**F533-DK**  
*Shown with Dark Walnut Blades  
Reversible to Medium Maple Blades*



**F533-WH**



**F533-BWH**



**F533-ORB**  
 Shown with Dark Walnut Blades  
 Reversible to Medium Maple Blades

## Mojo II

The Mojo II is another addition to our Value Collection featuring a wealth of performance and an integrated light source. A great value for low ceiling applications.

### FEATURES

- 14° Blade Pitch • 4-Blades 52" Sweep
- Flush Mount - Ideal for Low Ceilings Total Hanging Depth 13" with Light • 3-Speed Pull Chain
- Integrated Downlight Uses 3-60W Candelabra Bulbs (Included)
- Solid Cap and Finial Adaptation for Remote Control Use (Included)

### ENERGY INFORMATION (Excludes Lights)

- Airflow CFM: 5138 • Electricity Used Watts: 62.6 • Airflow Efficiency CFM/Watts: 82

**F533-ORB** • Oil Rubbed Bronze Finish • Reversible Medium Maple / Dark Walnut Blades • Tea Stain Glass

**F533-BN** • Brushed Nickel Finish • Reversible Medium Maple / Dark Walnut Blades • Frosted White Glass

**F533-DK** • Distressed Koa Finish • Reversible Medium Maple / Dark Walnut Blades • Tea Stain Glass

**F533-WH** • White Finish • White Blades • Frosted White Glass

**F533-BWH** • Bone White Finish • Bone White Blades • Bone White Glass



**F510-BS**



**F510-WH**

**F510-ORB**  
*See Opposite Page*

## SPACESAVER

Contemporary styling and superb air circulation for those smaller spaces in your home; perfect for kitchens and food preparation areas, bathrooms, walk-in closets and hallways.

### FEATURES

- 14° Blade Pitch • 3-Blades 26" Sweep
- Flush Mount - Ideal for Low Ceilings Total Hanging Depth 10¾" Drop from Ceiling
- 4-Speed Fan Full Range Dimmer 3-Wire Installation Wall Control Converts to Electronic Control - WC110 Included
- Integrated Halogen Light Uses 1-50W Mini-Can Halogen Bulb (Included)

### ENERGY INFORMATION (Excludes Lights)

- Airflow CFM: 2,132 • Electricity Used Watts: 30 • Airflow Efficiency CFM/Watts: 71.07

**F510-ORB** • Oil Rubbed Bronze Finish • Oil Rubbed Bronze Blades • Tinted Opal Glass

**F510-BS** • Brushed Steel Finish • Silver Blades • Etched Opal Glass

**F510-WH** • White Finish • White Blades • Etched Opal Glass



F510-ORB

minkaAire®

SPACESAVER 231



**F300-ORB**  
*Oscillating Fan*



**F300-BN**  
*Oscillating Fan*

## RETRO STYLE FAN

A special series of fans that go where you go. These portable fans offer the same style, quality and value you expect from

Minka-Aire® in a compact and portable design. An accent that is reminiscent of times past, our Retro Style Fan is your quiet companion; a stylistic, subtle, tabletop solution for your comfort needs in any room.

### FEATURES

- 4-Blade Turbofan 10" Sweep • 3 Speeds: 1,250, 1,400 and 1,500 R.P.M.
- Oscillates 70° Side to Side • Manual Tilt • Portable (Net Weight 7lbs.)
- 72" Heavy Duty Cord Length • Steel Construction • One Year Limited Warranty

**F300-ORB** • Oil Rubbed Bronze Finish • Oil Rubbed Bronze Blades

**F300-BN** • Brushed Nickel Finish • Brushed Nickel Blades



# CONTRACTOR UNI-PACK LED

with LED Light



**F656L-ORB**

*Shown with Dark Walnut Blades  
Reversible to Medium Maple Blades*



**F656L-PN**



**F656L-WH**



**F656L-BN/DW**  
 Shown with Dark Walnut Blades  
 Reversible to Medium Maple Blades

## CONTRACTOR UNI-PACK LED

with LED Light

A full feature LED Contractor 52-inch fan. Featuring the incredible 26 watt LED\*, 1,647 Lumens, 3,000 Kelvin light source and a 172 x 14mm heavy duty motor.

### FEATURES

- 12° Blade Pitch • 5-Blades 52" Sweep • 6" Downrod • 3-Speed Pull Chain
- Low Profile LED Light Uses 26W LED (Included) 3 Year Warranty • 1,647 Lumens • 3,000K • CRI 82
- Solid Cap and Finial Adaptation Kit for Remote Control Use (Included)

### ENERGY INFORMATION (Excludes Lights)

- Airflow CFM: 5,994 • Electricity Used Watts: 74.6 • Airflow Efficiency CFM/Watts: 80.35

- F656L-BN/DW** • Brushed Nickel Finish • Reversible Medium Maple / Dark Walnut Blades • Frosted White Glass
- F656L-ORB** • Oil Rubbed Bronze Finish • Reversible Medium Maple / Dark Walnut Blades • Frosted White Glass
- F656L-PN** • Polished Nickel Finish • Silver Blades • Frosted White Glass
- F656L-WH** • White Finish • White Blades • Frosted White Glass

# CONTRACTOR LED

with LED Light



**F556L-BN**



**F556L-BWH**



**F556L-BN/DW**

*Shown with Medium Maple Blades  
Reversible to Dark Walnut Blades*



**F556L-ORB**

*Shown with Medium Maple Blades  
Reversible to Dark Walnut Blades*

## CONTRACTOR LED

with LED Light

Smart simplicity at its best. This Contractor LED provides greater performance and offers energy efficiency through the use of the latest LED\* technology.

**FEATURES**

- 12° Blade Pitch • 5-Blades 52" Sweep • 6" Downrod • Hand Held Remote Control
- Integrated LED Light Uses 17W LED (Included) 3 Year Warranty • 1,100 Lumens • 3,000K • CRI 80
- Replacements LED Assembly (Part #6F844LK01)

**ENERGY INFORMATION** (Excludes Lights)

- Airflow CFM: 5,996 • Electricity Used Watts: 66.5 • Airflow Efficiency CFM/Watts: 89.71

- F556L-ORB** • Oil Rubbed Bronze Finish • Reversible Medium Maple / Dark Walnut Blades • Etched Lens
- F556L-BN** • Brushed Nickel Finish • Silver Blades • Etched Lens
- F556L-BWH** • Bone White Finish • Bone White Blades • Etched Lens
- F556L-BN/DW** • Brushed Nickel Finish • Reversible Medium Maple / Dark Walnut Blades • Etched Lens

# CONTRACTOR PLUS



**F556-BN**



**F556-BWH**



**F556-BN/DW**  
*Shown with Medium Maple Blades  
Reversible to Dark Walnut Blades*



**F556-ORB**  
Shown with Dark Walnut Blades  
Reversible to Medium Maple Blades

## CONTRACTOR PLUS

Our Contractor Plus fan continues our tradition of offering design and reliability in several finishes.

### FEATURES

- 12° Blade Pitch • 5-Blades 52" Sweep • 6" Downrod • 3-Speed Pull Chain
- Universal Light Kit Adaptable (Sold Separately. Page(s): 267)

### ENERGY INFORMATION (Excludes Lights)

- Airflow CFM: 5,966 • Electricity Used Watts: 66.5 • Airflow Efficiency CFM/Watts: 89.71

**F556-ORB** • Oil Rubbed Bronze Finish • Reversible Medium Maple / Dark Walnut Blades

**F556-BN** • Brushed Nickel Finish • Silver Blades

**F556-BWH** • Bone White Finish • Bone White Blades

**F556-BN/DW** • Brushed Nickel Finish • Reversible Medium Maple / Dark Walnut Blades

# ULTRA-MAX™



F588-SP-WH



F588-SP-ORB



F588-SP-BN





F588-SP-BCW

## ULTRA-MAX™

### FEATURES

- 14° Blade Pitch • 5-Blades 54" Sweep • 6" Downrod
- Full Function Wall Control System and Hand Held Remote Control
- Quick Connect Detachable Switch Cup
- Universal Light Kit Adaptable (Sold Separately. Page(s): 267)

### ENERGY INFORMATION (Excludes Lights)

- Airflow CFM: 4,834 • Electricity Used Watts: 51.5 • Airflow Efficiency CFM/Watts: 93.88

**F588-SP-BCW** • Belcaro Walnut™ Finish • Dark Walnut Blades

**F588-SP-WH** • White Finish • White Blades

**F588-SP-ORB** • Oil Rubbed Bronze Finish • Medium Maple Blades

**F588-SP-BN** • Brushed Nickel Finish • Dark Walnut Blades

# SUPRA<sup>®</sup> 52"

with Light Kit



F569-BS



F569-ORB



F569-WH



**F569-BS/DW**

## SUPRA<sup>®</sup> 52"

with Light Kit

A truly exceptional value! All the benefits of the Supra<sup>®</sup> 52" packaged with additional bells and whistles including a matching light kit and RCS223 Remote Control System.

### FEATURES

- 14° Blade Pitch • 5-Blades 52" Sweep • 6-Ply Warp Resistant Blades
- 6" Downrod • Hand Held Remote Control System
- Halogen Light Kit Uses 1-100W Mini-Can Halogen Bulb (Included)

### ENERGY INFORMATION (Excludes Lights)

- Airflow CFM: 5,755 • Electricity Used Watts: 79 • Airflow Efficiency CFM/Watts: 72.85

**F569-BS/DW** • Brushed Steel Finish • Dark Walnut Blades • Opal Glass

**F569-BS** • Brushed Steel Finish • Silver Blades • Opal Glass

**F569-ORB** • Oil Rubbed Bronze Finish • Medium Maple Blades • Opal Glass

**F569-WH** • White Finish • White Blades • Opal Glass



**F568-KA**

*Shown with Toned Medium Maple Blades  
Reversible to Medium Maple Blades*

## SUPRA<sup>®</sup> 52"

The Supra<sup>®</sup> 52" offers decorative versatility in multiple finishes. It has clean, modern styling and uncompromising quality with superior performance.

**FEATURES**

- 14° Blade Pitch • 5-Blades 52" Sweep • 6-Ply Warp Resistant Blades • 6" Downrod
- 3-Speed Pull Chain • Quick Connect Detachable Switch Cup
- Universal Light Kit Adaptable (Sold Separately. Page(s): 267)

Accessory Blades Available. See Page(s): 288

**ENERGY INFORMATION** (Excludes Lights)

- Airflow CFM: 5995.05 • Electricity Used Watts: 75.3 • Airflow Efficiency CFM/Watts: 79.62

**F568-KA** • Kocoa Finish • Reversible Toned Medium Maple / Medium Maple Blades

**F568-SWH** • Shell White Finish • Shell White Blades

**F568-BS/DW** • Brushed Steel Finish • Dark Walnut Blades

**F568-BWH** • Bone White Finish • Bone White Blades

# SUPRA<sup>®</sup> 52"



F568-SWH



F568-BS/DW



F568-BWH



# SUPRA® 52"



F568-WH



F568-BCW



F568-BS



F568-ORB

## SUPRA® 52"

- F568-ORB** • Oil Rubbed Bronze Finish • Medium Maple Blades
- F568-WH** • White Finish • White Blades
- F568-BCW** • Belcaro Walnut™ Finish • Dark Walnut Blades
- F568-BS** • Brushed Steel Finish • Silver Blades

# SUPRA® 44"

with Light Kit



F563-SP



F563-SP-BS/DW



F563-SP-WH



**F563-SP-ORB**

## SUPRA<sup>®</sup> 44"

with Light Kit

The Supra<sup>®</sup> 44", model F563-SP is a great economical option, packaged with a light kit to meet every need.

### FEATURES

- 14° Blade Pitch • 5-Blades 44" Sweep • 6-Ply Warp Resistant Blades • 6" Downrod
- 3-Speed Pull Chain • Halogen Light Kit Uses 1-100W Mini-Can Halogen Bulb (Included)

### ENERGY INFORMATION (Excludes Lights)

- Airflow CFM: 5,272 • Electricity Used Watts: 76 • Airflow Efficiency CFM/Watts: 69.37

**F563-SP-ORB** • Oil Rubbed Bronze Finish • Medium Maple Blades • Opal Glass

**F563-SP** • Brushed Steel Finish • Silver Blades • Opal Glass

**F563-SP-BS/DW** • Brushed Steel Finish • Dark Walnut Blades • Opal Glass

**F563-SP-WH** • White Finish • White Blades • Opal Glass



**F563-BS/DW**

## SUPRA® 44"

Designed with superior performance and all of the features found in full-size fans made available for mid-size rooms.

### FEATURES

- 14° Blade Pitch • 5-Blades 44" Sweep • 6-Ply Warp Resistant Blades • 6" Downrod
- 3-Speed Pull Chain • Quick Connect Detachable Switch Cup
- Universal Light Kit Adaptable (Sold Separately. Page(s): 267)

Accessory Blades Available. See Page(s): 288

### ENERGY INFORMATION (Excludes Lights)

- Airflow CFM: 5,272 • Electricity Used Watts: 76 • Airflow Efficiency CFM/Watts: 69.37

**F563-BS/DW** • Brushed Steel Finish • Dark Walnut Blades

**F563-ORB** • Oil Rubbed Bronze Finish • Medium Maple Blades

**F563-WH** • White Finish • White Blades

**F563-BS** • Brushed Steel Finish • Silver Blades

# SUPRA<sup>®</sup> 44"



F563-ORB



F563-WH



F563-BS



F562-BS

## SUPRA<sup>®</sup> 32"

Fashion, form and function for the smallest areas are highlighted in the Supra<sup>®</sup> 32". The perfect choice for bathrooms, hallways, entries and walk-in closets.

### FEATURES

- 22° Blade Pitch • 6-Blades 32" Sweep • 6-Ply Warp Resistant Blades • 6" Downrod
- 3-Speed Pull Chain • Quick Connect Detachable Switch Cup
- Universal Light Kit Adaptable (Sold Separately. Page(s): 267)

Accessory Blades Available. See Page(s): 288

### ENERGY INFORMATION (Excludes Lights)

- Airflow CFM: 4,075 • Electricity Used Watts: 66 • Airflow Efficiency CFM/Watts: 61.73

**F562-BS** • Brushed Steel Finish • Silver Blades

**F562-WH** • White Finish • White Blades

**F562-ORB** • Oil Rubbed Bronze Finish • Medium Maple Blades

# SUPRA<sup>®</sup> 32"



F562-WH



F562-ORB



F647-BS

## CONTRACTOR UNI-PACK

with 3-Light Kit

Offering affordable performance and reliability with designer finishes, the Contractor fan now comes with an integrated light kit.

### FEATURES

- 12° Blade Pitch • 4 or 5-Blades 52" Sweep • 6" Downrod • 3-Speed Pull Chain
- Integrated Light Kit Uses 3-60W Candelabra Bulbs (Included)

Accessory Blades Available. See Page(s): 288

### ENERGY INFORMATION (Excludes Lights)

- Airflow CFM: 4,901 • Electricity Used Watts: 62 • Airflow Efficiency CFM/Watts: 79.05

- F647-BS** • Brushed Steel Finish • Dark Walnut Blades • Etched Glass
- F647-ORB/TS** • Oil Rubbed Bronze Finish • Medium Maple Blades • Tea Stain Glass
- F647-WH** • White Finish • White Blades • Etched Glass
- F647-ORB** • Oil Rubbed Bronze Finish • Medium Maple Blades • Etched Glass

# CONTRACTOR UNI-PACK

with 3-Light Kit



F647-ORB/TS



F647-WH



F647-ORB



F648-BS

## CONTRACTOR UNI-PACK

with Bowl Light Kit

Our most economical and efficient fan and light combination for the budget-conscious customer, helping to save money and protect the environment through energy efficient products.

### FEATURES

- 12° Blade Pitch • 4 or 5-Blades 52" Sweep • 6" Downrod • 3-Speed Pull Chain
- Bowl Light Kit (Included) Uses 2-13W Non-Dimmable GU24 Spiral CFL Bulbs (Included)
- Pre-Installed One-Piece Motor Blade Iron Gasket • Cap for Non-Light Use (Included)

### ENERGY INFORMATION (Excludes Lights)

- Airflow CFM: 5,408 • Electricity Used Watts: 65 • Airflow Efficiency CFM/Watts: 82.69

**F648-BS** • Brushed Steel Finish • Dark Walnut Blades • Etched Swirl Glass

**F648-ORB/EX** • Oil Rubbed Bronze Finish • Medium Maple Blades • Excavation Glass

**F648-WH** • White Finish • White Blades • Etched Swirl Glass

**F648-ORB** • Oil Rubbed Bronze Finish • Medium Maple Blades • Etched Swirl Glass

# CONTRACTOR UNI-PACK

with Bowl Light Kit



F648-ORB/EX



F648-WH



F648-ORB

# CONTRACTOR UNI-PACK

with Bowl Light Kit



**F548-WH**



**F548-ORB**



**F548-ORB/EX**

## CONTRACTOR UNI-PACK

with Bowl Light Kit

The most economical and efficient fan and light combination for the secondary rooms in the house.

### FEATURES

- 12° Blade Pitch • 4 or 5-Blades 52" Sweep • 6" Downrod • 3-Speed Pull Chain
- Bowl Light Kit (Included) Uses 3-60W Candelabra Bulbs (Included)
- Pre-Installed One-Piece Motor Blade Iron Gasket • Cap for Non-Light Use (Included)

Accessory Blades Available. See Page(s): 288

### ENERGY INFORMATION (Excludes Lights)

- Airflow CFM: 4,636 • Electricity Used Watts: 64 • Airflow Efficiency CFM/Watts: 73.01

**F548-ORB/EX** • Oil Rubbed Bronze Finish • Medium Maple Blades • Excavation Glass

**F548-WH** • White Finish • White Blades • Etched Swirl Glass

**F548-ORB** • Oil Rubbed Bronze Finish • Medium Maple Blades • Etched Swirl Glass

# CONTRACTOR UNI-PACK

with Bowl Light Kit



F548-BS



F548-BWH



**F548-BS/DW**

## CONTRACTOR UNI-PACK

with Bowl Light Kit

The most economical and efficient fan and light combination for the secondary rooms in the house.

### FEATURES

- 12° Blade Pitch • 4 or 5-Blades 52" Sweep • 6" Downrod • 3-Speed Pull Chain
- Bowl Light Kit (Included) Uses 3-60W Candelabra Bulbs (Included)
- Pre-Installed One-Piece Motor Blade Iron Gasket • Cap for Non-Light Use (Included)

Accessory Blades Available. See Page(s): 288

### ENERGY INFORMATION (Excludes Lights)

- Airflow CFM: 4,636 • Electricity Used Watts: 64 • Airflow Efficiency CFM/Watts: 73.01

- F548-BS/DW** • Brushed Steel Finish • Dark Walnut Blades • Etched Swirl Glass
- F548-BS** • Brushed Steel Finish • Silver Blades • Etched Swirl Glass
- F548-BWH** • Bone White Finish • Bone white Blades • Etched Swirl Glass



**F547-ORB**

## CONTRACTOR 52"

Our Contractor series offers affordable performance and reliability. Designer finishes have been made available to match current trends and demands.

### FEATURES

- 12° Blade Pitch • 4 or 5-Blades 52" Sweep • 6" Downrod (Uses  $\frac{3}{4}$ " I.D. DR5 Series Downrod)
- 3-Speed Pull Chain • Quick Connect Detachable Switch Cup
- Pre-Installed One-Piece Motor/Blade Iron Gasket
- Universal Light Kit Adaptable (Sold Separately. Page(s): 267)

Accessory Blades Available. See Page(s): 288

### ENERGY INFORMATION (Excludes Lights)

- Airflow CFM: 4,565 • Electricity Used Watts: 61 • Airflow Efficiency CFM/Watts: 74.84

**F547-ORB** • Oil Rubbed Bronze Finish • Medium Maple Blades

**F547-BS/DW** • Brushed Steel Finish • Dark Walnut Blades

**F547-BWH** • Bone White Finish • Bone White Blades

**F547-BS** • Brushed Steel Finish • Silver Blades

**F547-WH** • White Finish • White Blades

# CONTRACTOR 52"



F547-BS/DW



F547-BWH



F547-BS



F547-WH

# CONTRACTOR 42"



**F546-ORB**



**F546-BS**



**F546-WH**



F546-BS/DW

## CONTRACTOR 42"

Our Contractor 42" series offers affordable performance and reliability. Designer finishes have been made available to match current trends and demand.

### **FEATURES**

- 12° Blade Pitch • 5-Blades 42" Sweep • 6" Downrod • 3-Speed Pull Chain
- Quick Connect Detachable Switch Cup • Pre-Installed One-Piece Motor/Blade Iron Gasket
- Universal Light Kit Adaptable (Sold Separately. Page(s): 267)

### **ENERGY INFORMATION** (Excludes Lights)

- Airflow CFM: 3,290 • Electricity Used Watts: 47 • Airflow Efficiency CFM/Watts: 70.01

- F546-BS/DW** • Brushed Steel Finish • Dark Walnut Blades
- F546-ORB** • Oil Rubbed Bronze Finish • Medium Maple Blades
- F546-BS** • Brushed Steel Finish • Silver Blades
- F546-WH** • White Finish • White Blades



**F565-WH 52"**



**F566-WH 42"**

## MESA

Our close-to-ceiling economy model in two sizes will move air in the tightest places.

### **FEATURES**

- 12° Blade Pitch • 5-Blades 52" or 42" Sweep • Flush Mount 8 $\frac{3}{4}$ " Overall Ceiling Drop
- 3-Speed Pull Chain • One-Piece Stamped Body • Quick Connect Detachable Switch Cup
- Universal Light Kit Adaptable (Sold Separately. Page(s): 267)

### **F565 ENERGY INFORMATION** (Excludes Lights)

- Airflow CFM: 5,092 • Electricity Used Watts: 66 • Airflow Efficiency CFM/Watts: 78

### **F566 ENERGY INFORMATION** (Excludes Lights)

- Airflow CFM: 3,291 • Electricity Used Watts: 50 • Airflow Efficiency CFM/Watts: 65.82

- F565-WH 52"** • White Finish • White Blades
- F566-WH 42"** • White Finish • White Blades







# UNIVERSAL LIGHT KITS

**K37**

Four Light  
40W Candelabra Base (Included)  
2 ¼" Side Shade  
13"Dia. x 6 ½"H

**K37-L-BCW****K1**

Four Light  
40W Candelabra Base (Included)  
2 ¼" Side Fitter  
11 ¾"Dia. x 3"H

**K1-L-BCW****K1-L-BS****K1-L-ORB****K1-L-44****K1099**

One Light  
Opal Glass  
60W Candelabra Base (Included)  
8 ½"Dia. x 6 ¾"H

**K1099-1-L-44**

**K9365-L-44 (Low Profile)**  
Three Light  
Etched Marble  
60W Candelabra Base (Included)  
12 ½"Dia. x 4 ½"H



**GC900 SET**  
Optional Crystal Set  
Available Only for the F900 Fan



*Please Note: All Light Kits Include Chain  
with Decorative Fob. (Not Shown)*

**Finish Codes**

BCW	Belcaro Walnut™	ORB	Oil Rubbed Bronze
BS	Brushed Steel	SWH	Shell White



# UNIVERSAL LIGHT KITS



## K34

Four Light  
13W Spiral Medium Base  
(Included)  
2 1/4" Side Shade  
11 3/4"Dia. x 2 3/4"H



K34-BN



K34-BCW



K34-BS



K34-CC



K34-DBB



K34-KA



K34-MCG



K34-ORB



K34-PI



K34-PW



K34-SWH



K34-44

### Finish Codes

BN Brushed Nickel  
BCW Dark Brushed Bronze  
BS Brushed Steel  
CC Cognac

DBB Dark Brushed Bronze  
KA Kocoo  
MCG Mottled Copper w/Gold  
ORB Oil Rubbed Bronze

PI Patina Iron  
PW Pewter  
SWH Shell White  
WH/44 White



# 2 1/4" GLASS SHADES



**2018A**  
Opal  
4 3/4"Dia. x 4 1/2"H



\* **2548**  
Etched Opal  
5 3/4"Dia. x 4 1/2"H



\* **2549**  
Etched Marble  
5 3/4"Dia. x 4 1/2"H



\* **2560**  
Frosted/Clear  
5"Dia. x 4 3/4"H



**2565**  
Etched Seeded  
4 3/4"Dia. x 4 3/4"H



\* **2593-1**  
Aged Champagne  
5"Dia. x 5 1/4"H



\* **2593-2**  
Excavation  
5"Dia. x 5 1/4"H



\* **2593-4**  
Venetian Scavo  
5"Dia. x 5 1/4"H



\* **2593-5**  
French Cream  
5"Dia. x 5 1/4"H



**2632**  
Salon Scavo™  
5"Dia. x 4 3/4"H



**2636**  
Tuscan Scavo  
5"Dia. x 4 3/4"H



**2645**  
Linen  
5"Dia. x 5 1/4"H



**2646**  
Tuscan Scavo  
5"Dia. x 5 1/4"H



**2652**  
Etched Marble  
5"Dia. x 4 3/4"H



**4099**  
4" Opal Glass  
Shade  
8 1/2"Dia. x 5 1/2"H

# CUSTOM LED LIGHT KITS



**K9838L-DK**



**K9838L-SL**



**K9838L-WH**

## **K9838L**

LED Light  
15W LED (Incl.)  
6½" Dia. x 1¾" H  
1,300 Lumens  
3,000 Kelvin  
CRI 80

Compatible with the  
F838L Force Fans Only



**K9886L-BNW**



**K9886L-ORB**



**K9886L-WHF**



**K9886L-SI**

## **K9886L**

LED Light  
20W LED (Incl.)  
6½" Dia. x 1¾" H  
1,430 Lumens  
3,000 Kelvin  
CRI 80

Compatible with the  
F886 Xtreme H<sub>2</sub>O Fans Only



**K9787L-ORB**



**K9787L-SL**



**K9787L-WHF**

## **K9787L**

LED Light  
15W LED (Incl.)  
5" Dia. x 1½" H  
1,300 Lumens  
3,000 Kelvin  
CRI 80

Compatible with the  
F787 Simple Fans Only

### **Finish Codes**

BNW	Brushed Nickel Wet	PBL	Provencal Blanc	SI	Smoked Iron
DK	Distressed Koa	PI	Patina Iron	WH/44	White
ORB	Oil Rubbed Bronze	PW	Pewter	WHF	Flat White





**WCS212  
Full Function  
AireControl®  
256 Bit**

- Three Speed Fan Control in Forward and Reverse
- On/Off Plus Full Range Light Dimmer with Independent Up/Downlight Control
- Includes One (1) Hand Held Remote Control, Wall Holster
- Wireless Remote Operation
- Operates at Distance of 20-40' Distance; Depends on Quality/Materials Used in Construction of Room/Building Fan is Hung In
- Can be Used in Conjunction with WCS212 Wall Mount AireControl®
- 12 Volt Battery Included
- Includes Brown, Ivory and White Finish Inner/Outer Plates

U.S. Patent(s): D533,514; 8,253,272



**WCS213  
AireControl®  
256 Bit**

- Three Speed Fan Control
- On/Off Plus Full Range Light Dimmer
- Includes One (1) Hand Held Remote Control, Wall Holster
- Wireless Remote Operation
- Operates at Distance of 20-40' Distance; Depends on Quality/Materials Used in Construction of Room/Building Fan is Hung In
- Can be Used in Conjunction with WCS223 Wall AireControl®
- 12 Volt Battery Included
- Includes Brown, Ivory and White Finish Inner/Outer Plates

U.S. Patent(s): D533,514; 8,253,272



**WCS223  
AireControl®  
256 Bit**

- Three Speed Fan Control
- On/Off Plus Full Range Light Dimmer
- Includes One (1) Hand Held Remote Control, Wall Holster and Canopy Mounted Receiver
- Wireless Remote Operation
- Operates at Distance of 20-40' Distance; Depends on Quality/Materials Used in Construction of Room/Building Fan is Hung In
- Can be Used in Conjunction with WCS213 Wall AireControl®
- 12 Volt Battery Included
- Includes Brown, Ivory and White Finish Inner/Outer Plates

U.S. Patent(s): D533,514; 8,253,272



Full Function Hand Held Remote Control

An ultra-thin design exclusive to Minka-Aire®, the remote enables the user with one finger to control all functions of Minka-Aire® ceiling fans.

AireControl® by Minka-Aire® controls all functions: reverse, upright (where applicable), fan light, speed control, as well as off-on (RCS212 and WCS212)

RCS213, RCS223, WCS213 and WCS223 controls do not include the reverse function.

Included is a holster if you want to wall mount the control for your convenience.



**WC400**  
**AireControl**<sup>®</sup>

- For F726, F787L, F823, F828, F838L, F886, F887, F888 and F889 Fans Only
- Six Speed Fan Control in Forward and Reverse
- On/Off Plus Full Range Light Dimmer
- Includes One (1) Hand Held Remote Control, Wall Holster
- Wireless Remote Operation
- Operates at Distance of 23' Distance; Depends on Quality/ Materials Used in Construction of Room/Building Fan is Hung In
- Includes Brown, Ivory and White Finish Inner/Outer Plates

U.S. Patent(s): D533,514



**WC500**  
**AireControl**<sup>®</sup>

- For F737, F853 and F853L Fans Only
- Six Speed Fan Control in Forward and Reverse
- On/Off Plus Full Range Light Dimmer
- Includes One (1) Hand Held Remote Control, Wall Holster
- Wireless Remote Operation
- Operates at Distance of 23' Distance; Depends on Quality/ Materials Used in Construction of Room/Building Fan is Hung In
- Includes Brown, Ivory and White Finish Inner/Outer Plates

U.S. Patent(s): D533,514



**WC600**  
**AireControl**<sup>®</sup>

- For F617L, F745, F899L and F905 Fans Only
- Six Speed Fan Control in Forward and Reverse
- On/Off Plus Full Range Light Dimmer
- Includes One (1) Hand Held Remote Control, Wall Holster
- Wireless Remote Operation
- Operates at Distance of 23' Distance; Depends on Quality/ Materials Used in Construction of Room/Building Fan is Hung In
- Includes Brown, Ivory and White Finish Inner/Outer Plates

U.S. Patent(s): D533,514



**WC105-WH**  
**Speed Control**

- Four Speed Fan Control
- 2-Wire Installation



**WC115**  
**Speed Control**

- For F624 Fans Only
- Four Speed Fan Control
- 2-Wire Installation



**WC106-WH**  
**Speed Control**

- Four Speed Fan Control
- Full Range Dimmer
- 3-Wire Installation



**WC110**  
**Speed Control**

- For F510 Fans Only
- Four Speed Fan Control
- Full Range Dimmer
- 3-Wire Installation



**WC116**  
**Speed Control**

- For F727 Fans Only
- Four Speed Fan Control
- Full Range Dimmer
- 3-Wire Installation





























































**Contractor 42"**  
F546  
Pages 264 - 265



**Contractor 52"**  
F547  
Pages 262 - 263



**Contractor LED**  
F556L  
Pages 236 - 237



**Contractor Plus**  
F556  
Pages 238 - 239



**Contractor Uni-Pack**  
F548  
Pages 258 - 261



**Contractor Uni-Pack**  
F647  
Pages 254 - 255



**Contractor Uni-Pack**  
F648  
Pages 256 - 257



**Contractor Uni-Pack LED**  
F656L  
Pages 234 - 235



**Craftsman™**  
F840  
Page 213



**Cristafano™**  
F900  
Page 160 - 161



**Delano®**  
F701  
Pages 124 - 125



**Delano® II**  
F711  
Pages 126 - 127



**Dyno**  
F1000  
Pages 220 - 221



**Elemental Gyro™**  
F306L  
Page 114 - 115




**Ellipse**  
F618L  
Pages 84 - 85



**Flyte®**  
F531  
Pages 62 - 63



**Force**  
F838L  
Pages 40 - 41



**Gauguin™**  
F581  
Pages 210 - 211



**Gilera**  
F733  
Pages 78 - 79



**Great Room Traditional**  
F539  
Pages 120 - 123



**Groton**  
F681  
Pages 174 - 175



**Gyrette™**  
F302  
Page 117



**Gyro™**  
F602  
Page 111



**Gyro™ Wet**  
F402  
Pages 112 - 113, 170 - 171



**Java**  
F753  
Pages 76 - 77, 190 - 191



**Java LED**  
F753L  
Pages 74 - 75, 188 - 189



**Kafé**  
F695  
Pages 142 - 145



**Kafé-XL**  
F696  
Pages 138 - 141



**Kewl**  
F833  
Pages 86 - 87



**Kola**  
F688  
Pages 136 - 137



**Kola-XL**  
F689  
Pages 134 - 135



**Light Wave**  
F844  
Pages 66 - 67



**Lineage™**  
F812  
Page 149



**Lun-Aire**  
F534L  
Page 216 - 217



**Mesa™**  
F565/F566  
Page 266



**Mojo**  
F522  
Pages 226 - 227



**Mojo II**  
F533  
Pages 228 - 229



**Napoli™**  
F705  
Page 150



**Napoli™ II**  
F715  
Page 151



**New Era**  
F513  
Pages 104 - 105



**Ninety-Nine**  
F899L  
Pages 25 - 29



**Pancake**  
F738  
Pages 12 - 13



**Pancake XL LED**  
F739L  
Pages 8 - 11



**Rainman™**  
F582  
Pages 198 - 199



**Raptor**  
F617L  
Pages 6 - 7



**Retro Style Fan**  
F300  
Page 232



**Roto**  
F524  
Pages 64 - 65



**Roto XL**  
F624  
Pages 176 - 177



**Rudolph**  
F727  
Pages 218 - 219



**Sabot**  
F745  
Pages 60 - 61



**San Francisco<sup>®</sup>**  
F528/F529  
Pages 54 - 55



**Santa Lucia<sup>™</sup>**  
F820  
Page 148



**Shade**  
F683L  
Page 196 - 197



**Shangri-La<sup>®</sup>**  
F580  
Page 212



**Simple**  
F787  
Pages 56 - 57, 172 - 173



**Slipstream**  
F888  
Pages 14 - 15, 200 - 201



**Spacesaver**  
F510  
Pages 230 - 231



**Spectre**  
F726  
Pages 50 - 53



**Steal**  
F729  
Pages 222 - 223



**Strata**  
F734  
Pages 194 - 195



**Sundance™**  
F571/F572  
Pages 208 - 209



**Sundowner®**  
F589  
Pages 204 - 207



**Sunseeker**  
F532  
Pages 202 - 203



**Supra® 32"**  
F562  
Pages 252 - 253



**Supra® 44"**  
F563  
Pages 250 - 251



**Supra® 44" -SP**  
F563-SP  
Pages 248 - 249



**Supra® 52"**  
F568  
Pages 244 - 247



**Supra® 52"**  
F569  
Pages 242 - 243



**Symbio**  
F828  
Pages 72 - 73



**Timeless**  
F614  
Pages 128 - 133



**Traditional Concept™ 44"**  
F593  
Pages 96 - 97, 186 - 187



**Traditional Concept™ 52"**  
F594  
Pages 94 - 95, 184 - 185



**Traditional Gyro™**  
F502  
Page 110



**Traditional Mojo**  
F622  
Pages 224 - 225



**Uchiwa**  
F824  
Pages 98 - 99



**Ultra-Max™**  
F588-SP  
Pages 240 - 241



**Vintage Gyro™**  
F802  
Pages 108 - 109



**Volterra™**  
F702  
Page 158



**Wave**  
F843  
Pages 68 - 69



**Wing**  
F823  
Pages 58 - 59



**Xtreme**  
F887  
Pages 21 - 24



**Xtreme H<sub>2</sub>O**  
F886  
Pages 16 - 20, 166 - 169



**Zen**  
F514  
Pages 102 - 103









