



Architectural Princess















For color photos of finishes see
inside back cover.


















PRINCESS SHAPE

 listed 883C except where noted by asterisk(*).



















See page A84 for ordering
Custom Plates not found
in this listing.

	STAINLESS TYPE 302 (.035") Spec. Grade Satin Finish U.S. #32D (302SS-PRL)	SATIN BRASS (.040") Satin Finish U.S. #4 (4BB-PRL)	ALUMINUM (.050") Clear Anodized U.S. #28 (5AA-PRL)	SATIN BRONZE (.040") Satin Finish U.S. #10 (4SBR-PRL)	STAINLESS TYPE 430 (.030") Satin Finish U.S. #32D (SS-PRL)	UN- FINISHED STEEL Zinc Coat (AUNF- PRL)
 1 Toggle Switch (1T)	53071	54071	55071	56071	57071	80071
 2 Toggle Switches (2T)	53072	54072	55072	56072	57072	80072
 3 Toggle Switches (3T)	53073	54073	55073	56073	57073	80073
 4 Toggle Switches (4T)	53074	54074	55074	56074	57074	80074
 5 Toggle Switches (5T)	53075	54075	55075	56075	57075	
 6 Toggle Switches (6T)	53076	54076	55076	56076	57076	
 1 Duplex Receptacle (10DR)	53101	54101	55101	56101	57101	80101
 2 Duplex Receptacles (20DR)	53102	54102	55102	56102	57102	80102
 3 Duplex Receptacles (30DR)	53103	54103	55103	56103	57103	
 4 Duplex Receptacles (40DR)	53104	54104	55104	56104	57104	
 5 Duplex Receptacles (50DR)	53105	54105	55105	56105	57105	
 6 Duplex Receptacles (60DR)	53106	54106	55106	56106	57106	


















Architectural Princess

	STAINLESS TYPE 302 (.035")	SATIN BRASS (.040")	ALUMINUM (.050")	SATIN BRONZE (.040")	STAINLESS TYPE 430 (.030")	UN- FINISHED STEEL
 1 Single Recept. (1.405") (10R)	53091	54091	55091	56091	57091	80091
 2 Single Recepts. (1.405") (20R)	53092	54092	55092	56092	57092	
 1 Blank with Mounting Strap (Device Mntg. 2.375") (1BDE)	53121	54121	55121	56121	57121	
 2 Blanks with Mounting Straps (Device Mntg. 2.375") (2BDE)	53122	54122	55122	56122	57122	
 3 Blanks with Mounting Straps (3BDE)	53123	54123	55123	56123	57123	
 1 Blank (Box Mntg. 3.281") (1B)	53151	54151	55151	56151	57151	80151
 2 Blanks (Box Mntg. 3.281") (2B)	53152	54152	55152	56152	57152	80152
 3 Blanks (Box Mntg. 3.281") (3B)	53153	54153	55153	56153	57153	
 4 Blanks (Box Mntg. 3.281") (4B)	53154	54154	55154	56154	57154	
 5 Blanks (Box Mntg. 3.281") (5B)	53155	54155	55155	56155	57155	
 6 Blanks (Box Mntg. 3.281") (6B)	53156	54156	55156	56156	57156	
 Block Duplex/GFI Receptacle (SRM)	53401	54401	55401	56401	57401	80401
 2 Block Duplex/GFI Receptacles (2SRM)	53402	54402	55402	56402	57402	80402
 3 Block Duplex/GFI Receptacles (3SRM)	53403	54403	55403	56403	57403	80403
 4 Block Duplex/GFI Receptacles (4SRM)	53404	54404	55404	56404	57404	80404
 5 Block Duplex/GFI Receptacles (5SRM)	53405	54405	55405	56405	57405	80405
 6 Block Duplex/GFI Receptacles (6SRM)	53406	54406	55406	56406	57406	80406















Architectural • Princess

	STAINLESS TYPE 302 (.035")	SATIN BRASS (.040")	ALUMINUM (.050")	SATIN BRONZE (.040")	STAINLESS TYPE 430 (.030")	UN- FINISHED STEEL
 One 5/8" ID Phone (Box Mntg. 3.281") (01)*	53201	54201	55201	56201	57201	80201
 Two 5/8" ID Phones (Box Mntg. 3.281") (02)*	53202	54202	55202	56202	57202	
 One 5/8" ID Phone with Metal Bushing (Box Mntg. 3.281") (61)*	53591	54591	55591	56591	57591	
 One Phone .5" with .375" ID Grommet and Mounting Strap (Device Mntg. 2.375")*	53181	54181	55181	56181	57181	
 One Phone 1.405" with 1" ID Plastic Bushing (Box Mntg. 3.281") (71)*	53581	54581	55581	56581	57581	
 One 20A TL Recept. 1.620" ID Hole (3R)	53111	54111	55111	56111	57111	
 Two 20A TL Recepts. 1.620" ID Hole Must Use 3 Gang Plate (23R)	53113	54113	55113	56113	57113	
 One 30A 3 & 4 Wire TL Recept. 1.730" ID Hole (3330R)	53229	54229	55229	56229	57229	
 30/50A 3 Wire Range/Dryer Recept. 2.125" ID Hole (3D)	53221	54221	55221	56221	57221	
 30/50A 3 Wire Range/Dryer Recept. 2.125" ID Hole 2 Gang Plate (23D)	53222	54222	55222	56222	57222	
 30/50A 3 Wire Range/Dryer Recept. 2.125" ID Hole (N23D)	53227	54227	55227	56227	57227	
 30/50/60A 3 & 4 Wire Recepts. 2.480" ID Hole (5R)	53223	54223	55223	56223	57223	
 30/50/60A 4 Wire for Leviton 278 & 279 Recepts. 2.625" ID Hole (L5R)	53225	54225	55225	565225	57225	
 30/50/60A 4 Wire Offset Recepts., 2.275" ID Hole (N5RR)	53226	54226	55226	56226	57226	
 30/50/60A 4 Wire Recepts. 2.255" ID Hole (P5R)	53228	54228	55228	56228	57228	
 Louver, Horizontal (Device Mntg. 2.375") (LH)	53630	54630	55630	56630	57630	
 Louver, Vertical (Device Mntg. 2.375") (LV)	53631	54631	55631	56631	57631	
 2 Louvers (Device Mntg. 2.375") (2LV)	53632	54632	55632	56632	57632	

Architectural • Princess

	STAINLESS TYPE 302 (.035")	SATIN BRASS (.040")	ALUMINUM (.050")	SATIN BRONZE (.040")	STAINLESS TYPE 430 (.030")	UN- FINISHED STEEL
 Interchangeable 1 Hole Horizontal (71A)	53011X	54011X	55011X	56011X	57011X	
 Interchangeable 1 Hole Per Gang, Horizontal (72A)	53012X	54012X	55012X	56012X	57012X	
 Interchangeable 2 Holes (71B)	53021X	54021X	55021X	56021X	57021X	
 Interchangeable 2 Holes Per Gang (72B)	53022X	54022X	55022X	56022X	57022X	
 Interchangeable 2 Holes Per Gang (73B)	53023X	54023X	55023X	56023X	57023X	
 Interchangeable 3 Holes (71C)	53031X	54031X	55031X	56031X	57031X	
 Interchangeable 3 Holes Per Gang (72C)	53032X	54032X	55032X	56032X	57032X	
 Interchangeable 1 Hole Vertical (71G)	53041X	54041X	55041X	56041X	57041X	
 Interchangeable 1 Hole Horizontal, 2 Holes (71A-71B)	53052X	54052X	55052X	56052X	57052X	
 Toggle Switch, Duplex Recept. (1T-10DR)	53532	54532	55532	56532	57532	80532
 Toggle Switch, Interchangeable 2 Holes (1T-71B)	53062X	54062X	55062X	56062X	57062X	
 Toggle Switch, Interchangeable 3 Holes (1T-71C)	53132X	54132X	55132X	56132X	57132X	
 Toggle Switch, Single Recept. (1.405" ID Hole) (1T-71C)	53512	54512	55512	56512	57512	
 Toggle Switch, 5/8" ID Phone (Box Mntg. 3.281") (1T-01)	53472	54472	55472	56472	57472	
 Toggle Switch, Blank (Box Mntg. 3.281") (1T-1B)	53522	54522	55522	56522	57522	
 Toggle Switch, Block Duplex/GFI Recept. (1T-SRM)	53432	54432	55432	56432	57432	
 Duplex Recept., Blank (Box Mntg. 3.281") (10DR-1B)	53542	54542	55542	56542	57542	


Architectural • Princess

	STAINLESS TYPE 302 (.035")	SATIN BRASS (.040")	ALUMINUM (.050")	SATIN BRONZE (.040")	STAINLESS TYPE 430 (.030")	UN- FINISHED STEEL
 Duplex Recept., 1/8" ID Phone (Box Mntg. 3.281") (10DR-01)	53582	54582	55582	56582	57582	
 Duplex Recept., Single Recept. (1.405" ID Hole) (10DR-10R)	53572	54572	55572	56572	57572	
 Duplex Recept., Block Duplex/GFI Recept. (10DR-SRM)	53672	54672	55672	56672	57672	
 Duplex Recept., Interchangeable 2 Holes (10DR-71B)	53142X	54142X	55142X	56142X	57142X	
 Duplex Recept., Interchangeable 3 Holes (10DR-71C)	53172X	54172X	55172X	56172X	57172X	
 Duplex Recept., 20A TL Recept. (1.620" ID Hole) (10DR-3R)	53390	54390	55390	56390	57390	
 Duplex Recept., 30A Range/Dryer Recept. (2.125" ID Hole) (10DR-3D)	53180	54180	55180	56180	57180	
 Single Recept. (1.405" ID Hole) Blank (Box Mntg. 3.281") (10R-1B)	53552	54552	55552	56552	57552	
 Block Duplex/GFI Recept., Blank (Box Mntg. 3.281") (SRM-1B)	53422	54422	55422	56422	57422	
 Toggle Switch, Centered 2 Gang Plate (1T-2G)	53772	54772	55772	56772	57772	
 Duplex Recept., Centered 2 Gang Plate (10DR-2G)	53773	54773	55773	56773	57773	
 Single Recept., Centered 2 Gang Plate (1.405" ID Hole) (10R-2G)	53774	54774	55774	56774	57774	
 1/8" ID Phone (Box Mntg. 3.281"), Centered 2 Gang Plate (01-2G)	53775	54775	55775	56775	57775	
 2 Toggle Switches, Duplex Receptacle (2T-10DR)	53543	54543	55543	56543	57543	80543
 2 Toggle Switches, Blank (Box Mntg. 3.281") (2T-1B)	53533	54533	55533	56533	57533	
 2 Toggle Switches, Block Duplex/GFI Recept. (2T-SRM)	53443	54443	55443	56443	57443	
 Toggle Switch, 2 Block Duplex/GFI Recept. (1T-2SRM)	53453	54453	55453	56453	57453	

Architectural • Princess


	STAINLESS TYPE 302 (.035")	SATIN BRASS (.040")	ALUMINUM (.050")	SATIN BRONZE (.040")	STAINLESS TYPE 430 (.030")	UN- FINISHED STEEL
Toggle Switch, 2 Blanks (Box Mntg. 3.281") (1T-2B)	53133	54133	55133	56133	57133	
Toggle Switch, 2 Duplex Recepts. (1T-20DR)	53553	54553	55553	56553	57553	
Toggle Switch, Block Duplex, Duplex Recepts. (1T-SRM-10DR)	53503	54503	55503	56503	57503	
Duplex Recept., 2 Blanks (Box Mntg. 3.281") (10DR-2B)	53423	54423	55423	56423	57423	
Blank (Box Mntg. 3.281"), Duplex Recept., Blank (Box Mntg. 3.281") (1B-10DR-1B)	53193	54193	55193	56193	57193	
Blank (Box Mntg. 3.281"), 2 Duplex Recepts. (1B-20DR)	53163	54163	55163	56163	57163	
Single Recept. (1.405" ID Hole), 2 Duplex Recepts. (10R-20DR)	53593	54593	55593	56593	57593	
Toggle Switch, Blank (Box Mntg. 3.281"), Duplex Recept. (1T-1B-10DR)	53233	54233	55233	56233	57233	
3 Toggle Switches, Duplex Recept. (3T-10DR)	53554	54554	55554	56554	57554	
3 Toggle Switches, Block Duplex/GFI Recept. (3T-SRM)	53454	54454	55454	56454	57454	
3 Toggle Switches, Blank (Box Mntg. 3.281") (3T-1B)	53544	54544	55544	56544	57544	
2 Toggle Switches, 2 Duplex Recepts. (2T-20DR)	53564	54564	55564	56564	57564	
2 Toggle Switches, 2 Blanks (Box Mntg. 3.281") (2T-2B)	53574	54574	55574	56574	57574	
Toggle Switch, 3 Duplex Recepts. (1T-30DR)	53584	54584	55584	56584	57584	
2 Duplex Recepts., 2 Blanks (Box Mntg. 3.281") (20DR-2B)	53164	54164	55164	56164	57164	
4 Toggle Switches, Duplex Recept. (4T-10DR)	53565	54565	55565	56565	57565	
4 Toggle Switches, Block Duplex/GFI Recepts. (4T-SRM)	53465	54465	55465	56465	57465	
3 Toggle Switches, 2 Duplex Recepts. (3T-20DR)	53575	54575	55575	56575	57575	
5 Toggle Switches, Duplex Recept. (5T-10DR)	53576	54576	55576	56576	57576	

Residential & Commercial Wall Plates















For color photos of finishes see inside back cover.


















PRINCESS SHAPE

 listed 883C except where noted by asterisk(*).

See page A84 for ordering Custom Plates not found in this listing.

	SPRAYED BRASS MATTE	CHROME PLATED	IVORY SEMI-GLOSS	WHITE WRINKLE	WHITE SEMI-GLOSS	BROWN WRINKLE	IVORY WRINKLE
	Painted Steel (BA-PRL)	Polished Steel (CA-PRL)	Painted Steel (IA-PRL)	Painted Steel (DW-PRL)	Painted Steel (WA-PRL)	Painted Steel (DB-PRL)	Painted Steel (DI-PRL)
 1 Toggle Switch (1T)	71071	73071	74071	75071	76071	78071	79071
 2 Toggle Switches (2T)	71072	73072	74072	75072	76072	78072	79072
 3 Toggle Switches (3T)	71073	73073	74073	75073	76073	78073	79073
 4 Toggle Switches (4T)	71074	73074	74074	75074	76074	78074	79074
 5 Toggle Switches (5T)	71075	73075	74075	75075	76075	78075	79075
 6 Toggle Switches (6T)	71076	73076	74076	75076	76076	78076	79076
 1 Duplex Receptacle (10DR)	71101	73101	74101	75101	76101	78101	79101
 2 Duplex Receptacles (20DR)	71102	73102	74102	75102	76102	78102	79102
 3 Duplex Receptacles (30DR)	71103	73103	74103	75103	76103	78103	79103
 4 Duplex Receptacles (40DR)	71104	73104	74104	75104	76104	78104	79104
 5 Duplex Receptacles (50DR)	71105	73105	74105	75105	76105	78105	79105
 6 Duplex Receptacles (60DR)	71106	73106	74106	75106	76106	78106	79106

















Residential & Commercial Princess

	SPRAYED BRASS MATTE	CHROME PLATED	IVORY SEMI- GLOSS	WHITE WRINKLE	WHITE SEMI- GLOSS	BROWN WRINKLE	IVORY WRINKLE
 1 Single Recept. (1.405") (10R)	71091	73091	74091	75091	76091	78091	79091
 2 Single Recepts. (1.405") (20R)	71092	73092	74092	75092	76092	78092	79092
 1 Blank with Mounting Strap (Device Mntg. 2.375") (1BDE)	71121	73121	74121	75121	76121	78121	79121
 2 Blanks with Mounting Straps (Device Mntg. 2.375") (2BDE)	71122	73122	74122	75122	76122	78122	79122
 3 Blanks with Mounting Straps (Device Mntg. 2.375") (3BDE)	71123	73123	74123	75123	76123	78123	79123
 1 Blank (Box Mntg. 3.281") (1B)	71151	73151	74151	75151	76151	78151	79151
 2 Blanks (Box Mntg. 3.281") (2B)	71152	73152	74152	75152	76152	78152	79152
 3 Blank (Box Mntg. 3.281") (3B)	71153	73153	74153	75153	76153	78153	79153
 4 Blank (Box Mntg. 3.281") (4B)	71154	73154	74154	75154	76154	78154	79154
 5 Blank (Box Mntg. 3.281") (5B)	71155	73155	74155	75155	76155	78155	79155
 6 Blank (Box Mntg. 3.281") (6B)	71156	73156	74156	75156	76156	78156	79156
 Block Duplex/GFI Receptacle (SRM)	71401	73401	74401	75401	76401	78401	79401
 2 Block Duplex/GFI Receptacles (2SRM)	71402	73402	74402	75402	76402	78402	79402
 3 Block Duplex/GFI Receptacles (3SRM)	71403	73403	74403	75403	76403	78403	79403
 4 Block Duplex/GFI Receptacles (4SRM)	71404	73404	74404	75404	76404	78404	79404
 5 Block Duplex/GFI Receptacles (5SRM)	71405	73405	74405	75405	76405	78405	79405
 6 Block Duplex/GFI Receptacles (6SRM)	71406	73406	74406	75406	76406	78406	79406


















Residential & Commercial Princess

	SPRAYED BRASS MATTE	CHROME PLATED	IVORY SEMI- GLOSS	WHITE WRINKLE	WHITE SEMI- GLOSS	BROWN WRINKLE	IVORY WRINKLE
 One 1/4" ID Phone (Box Mntg. 3.281") (01)"	71201	73201	74201	75201	76201	78201	79201
 Two 1/4" ID Phones (Box Mntg. 3.281") (02)"	71202	73202	74202	75202	76202	78202	79202
 One 1/4" ID Phone with Metal Bushing (Box Mntg. 3.281") (61)"	71591	73591	74591	75591	76591	78591	79591
 One Phone with .375" ID Grommet and Mounting Strap (Device Mntg. 2.375")	71181	73181	74181	75181	76181	78181	79181
 One Phone 1.405" with 1" ID Plastic Bushing (Box Mntg. 3.281") (71)"	71581	73581	74581	75581	76581	78581	79581
 One 20A TL Recept. 1.620" ID Hole (3R)	71111	73111	74111	75111	76111	78111	79111
 Two 20A TL Recepts. 1.620" ID Hole Must Use 3 Gang Plate (23R)	71113	73113	74113	75113	76113	78113	79113
 One 30A 3 & 4 Wire TL Recept. 1.730" ID Hole (333OR)	71229	73229	74229	75229	76229	78229	79229
 30/50A 3 Wire Range/Dryer Recept. 2.125" ID Hole (3D)	71221	73221	74221	75221	76221	78221	79221
 30/50A 3 Wire, Range/Dryer Recept. 2.125" ID Hole 2 Gang Plate (23D)	71222	73222	74222	75222	76222	78222	79222
 30/50A 3 Wire Range/Dryer Recept. 2.125" ID Hole (N23D)	71227	73227	74227	75227	76227	78227	79227
 30/50/60A 3 & 4 Wire Recepts. 2.480" ID Hole (5R)	71223	73223	74223	75223	76223	78223	79223
 30/50/60A 4 Wire for Leviton 278 & 279 Recepts. 2.625" ID Hole (L5R)	71225	73225	74225	75225	76225	78225	79225
 30/50/60A 4 Wire Offset Recepts., 2.275" ID Hole (N5RR)	71226	73226	74226	75226	76226	78226	79226
 30/50/60A 4 Wire Recepts. 2.255" ID Hole (P5R)	71228	73228	74228	75228	76228	78228	79228
 Louver, Horizontal (Device Mntg. 2.375") (LH)	71630	73630	74630	75630	76630	78630	79630
 Louver, Vertical (Device Mntg. 2.375") (LV)	71631	73631	74631	75631	76631	78631	79631
 2 Louvers (Device Mntg. 2.375") (2LV)	71632	73632	74632	75632	76632	78632	79632

Residential & Commercial Princess

	SPRAYED BRASS MATTE	CHROME PLATED	IVORY SEMI- GLOSS	WHITE WRINKLE	WHITE SEMI- GLOSS	BROWN WRINKLE	IVORY WRINKLE
 Interchangeable 1 Hole Horizontal (71A)	71011X	73011X	74011X	75011X	76011X	78011X	79011X
 Interchangeable 1 Hole Per Gang, Horizontal (72A)	71012X	73012X	74012X	75012X	76012X	78012X	79012X
 Interchangeable 2 Holes (71B)	71021X	73021X	74021X	75021X	76021X	78021X	79021X
 Interchangeable 2 Holes Per Gang (72B)	71022X	73022X	74022X	75022X	76022X	78022X	79022X
 Interchangeable 2 Holes Per Gang (73B)	71023X	73023X	74023X	75023X	76023X	78023X	79023X
 Interchangeable 3 Holes (71C)	71031X	73031X	74031X	75031X	76031X	78031X	79031X
 Interchangeable 3 Holes Per Gang (72C)	71032X	73032X	74032X	75032X	76032X	78032X	79032X
 Interchangeable 1 Hole Vertical (71G)	71041X	73041X	74041X	75041X	76041X	78041X	79041X
 Interchangeable 1 Hole Horizontal, 2 Holes (71A-71B)	71052X	73052X	74052X	75052X	76052X	78052X	79052X
 Toggle Switch, Duplex Recept. (1T-10DR)	71532	73532	74532	75532	76532	78532	79532
 Toggle Switch, Interchangeable 2 Holes (1T-71B)	71062X	73062X	74062X	75062X	76062X	78062X	79062X
 Toggle Switch, Interchangeable 3 Holes (1T-71C)	71132X	73132X	74132X	75132X	76132X	78132X	79132X
 Toggle Switch, Single Recept. (1.405" ID Hole) (1T-10R)	71512	73512	74512	75512	76512	78512	79512
 Toggle Switch, 5/8" ID Phone (Box Mntg. 3.281") (1T-01)	71472	73472	74472	75472	76472	78472	79472
 Toggle Switch, Blank (Box Mntg. 3.281") (1T-1B)	71522	73522	74522	75522	76522	78522	79522
 Toggle Switch, Block Duplex/GFI Recept. (1T-SRM)	71432	73432	74432	75432	76432	78432	79432
 Duplex Recept., Blank (Box Mntg. 3.281") (10DR-1B)	71542	73542	74542	75542	76542	78542	79542

Residential & Commercial Princess

	SPRAYED BRASS MATTE	CHROME PLATED	IVORY SEMI- GLOSS	WHITE WRINKLE	WHITE SEMI- GLOSS	BROWN WRINKLE	IVORY WRINKLE
 Duplex Recept., 5/8" ID Phone (Box Mntg. 3.281") (10DR-01)	71582	73582	74582	75582	76582	78582	79582
 Duplex Recept., Single Recept. (1.405" ID Hole) (10DR-10R)	71572	73572	74572	75572	76572	78572	79572
 Duplex Recept., Block Duplex/GFI Recept. (10DR-SRM)	71672	73672	74672	75672	76672	78672	79672
 Duplex Recept., Interchangeable 2 Holes (10DR-71B)	71142X	73142X	74142X	75142X	76142X	78142X	79142X
 Duplex Recept., Interchangeable 3 Holes (10DR-71C)	71172X	73172X	74172X	75172X	76172X	78172X	79172X
 Duplex Recept., 20A TL Recept. (1.620" ID Hole) (10DR-3R)	71390	73390	74390	75390	76390	78390	79390
 Duplex Recept., 30A Range/Dryer Recept. (2.125" ID Hole) (10DR-3D)	71180	73180	74180	75180	76180	78180	79180
 Single Recept. (1.405" ID Hole) Blank (Box Mntg. 3.281") (10R-1B)	71552	73552	74552	75552	76552	78552	79552
 Block Duplex/GFI Recept., Blank (Box Mntg. 3.281") (SRM-1B)	71422	73422	74422	75422	76422	78422	79422
 Toggle Switch, Centered 2 Gang Plate (1T-2G)	71772	73772	74772	75772	76772	78772	79772
 Duplex Recept., Centered 2 Gang Plate (10DR-2G)	71773	73773	74773	75773	76773	78773	79773
 Single Recept., (1.405" ID Hole) Centered 2 Gang Plate (10R-2G)	71774	73774	74774	75774	76774	78774	79774
 5/8" ID Phone (Box Mntg. 3.281"), Centered 2 Gang Plate (01-2G)	71775	73775	74775	75775	76775	78775	79775
 2 Toggle Switches, Duplex Receptacle (2T-10DR)	71543	73543	74543	75543	76543	78543	79543
 2 Toggle Switches, Blank (Box Mntg. 3.281") (2T-1B)	71533	73533	74533	75533	76533	78533	79533
 2 Toggle Switches, Block Duplex/GFI Recept. (2T-SRM)	71443	73443	74443	75443	76443	78443	79443
 Toggle Switch, 2 Block Duplex/GFI Recepts. (1T-2SRM)	71453	73453	74453	75453	76453	78453	79453

Residential & Commercial Princess

	SPRAYED BRASS MATTE	CHROME PLATED	IVORY SEMI- GLOSS	WHITE WRINKLE	WHITE SEMI- GLOSS	BROWN WRINKLE	IVORY WRINKLE
Toggle Switch, 2 Blanks (Box Mntg. 3.281") (1T-2B)	71133	73133	74133	75133	76133	78133	79133
Toggle Switch, 2 Duplex Recepts. (1T-20DR)	71553	73553	74553	75553	76553	78553	79553
Toggle Switch, Block Duplex, Duplex Recepts. (1T-SRM-10DR)	71503	73503	74503	75503	76503	78503	79503
Duplex Recept., 2 Blanks (Box Mntg. 3.281") (10DR-2B)	71423	73423	74423	75423	76423	78423	79423
Blank (Box Mntg. 3.281"), Duplex Recept., Blank (Box Mntg. 3.281") (1B-10DR-1B)	71193	73193	74193	75193	76193	78193	79193
Blank (Box Mntg. 3.281"), 2 Duplex Recepts. (1B-20DR)	71163	73163	74163	75163	76163	78163	79163
Single Recept. (1.405" ID Hole), 2 Duplex Recepts. (10R-20DR)	71593	73593	74593	75593	76593	78593	79593
Toggle Switch, Blank (Box Mntg. 3.281"), Duplex Recept. (1T-1B-10DR)	71233	73233	74233	75233	76233	78233	79233
3 Toggle Switches, Duplex Recept. (3T-10DR)	71554	73554	74554	75554	76554	78554	79554
3 Toggle Switches, Block Duplex/GFI Recept. (3T-SRM)	71454	73454	74454	75454	76454	78454	79454
3 Toggle Switches, Blank (Box Mntg. 3.281") (3T-1B)	71544	73544	74544	75544	76544	78544	79544
2 Toggle Switches, 2 Duplex Recepts. (2T-20DR)	71564	73564	74564	75564	76564	78564	79564
2 Toggle Switches, 2 Blanks (Box Mntg. 3.281") (2T-2B)	71574	73574	74574	75574	76574	78574	79574
Toggle Switch, 3 Duplex Recepts. (1T-30DR)	71584	73584	74584	75584	76584	78584	79584
2 Duplex Recepts., 2 Blanks (Box Mntg. 3.281") (20DR-2B)	71164	73164	74164	75164	76164	78164	79164
4 Toggle Switches, Duplex Recept. (4T-10DR)	71565	73565	74565	75565	76565	78565	79565
4 Toggle Switches, Block Duplex/GFI Recepts. (4T-SRM)	71465	73465	74465	75465	76465	78465	79465
3 Toggle Switches, 2 Duplex Recepts. (3T-20DR)	71575	73575	74575	75575	76575	78575	79575
5 Toggle Switches, Duplex Recept. (5T-10DR)	71576	73576	74576	75576	76576	78576	79576