

**Cord Sets**

**Fixture Whips**

**Temporary Lighting**



**2014-2015**

Lighting, Electrical &  
Cord Set Products

**Tube Guards**

**Lamp Holders**



*B-Lite at a glance*

- Labor saving unit comes fully assembled
- Multi-Tap ballast: 120v, 208v, 240v, 277v (factory wired 120v)
- 400w, clear MH Pulse Start lamp (included) meets OSHA1926.56 for minimum illumination of work areas (minimum of 5 foot-candles for general construction area lighting) when mounted 15' above 40' x 40' & 60' x 60' bays

*Features*



Two .75" knockouts for conduit access. (One knockout on opposite side) for "daisy chain" of multiple fixtures

*New Full Color Box*



Easy Carry Handle

Snap Lock Hook "Self Locking"



B-Lite<sup>®</sup>

Steel housing, white powdercoat finish

Open air ballast housing to reduce temperature & overheating

Type "O" spring loaded PINK porcelain screw shell socket

3ft. power cord #18/3 SJTOW with NEMA 5-15120V, 15amp plug

400W MH Pulse Start Type "O" Lamp

Heavy duty corrosion resistant welded steel safety cage

Open-Close bottom guard 9.45" opening for easy re-lamping



**Cat# BLite-400PS**


- Meets **OSHA** requirements for minimum illumination of work areas when properly installed
- Meets **EISA 2007** for energy efficiency
- Meets **NEC 2005** and 2008 requirements



HIGH BAY WORK LIGHT



# CONTRACTOR SERIES



**ALL YELLOW UNIT**

## Contractor Grade Temporary Light Stringer

GL-100MPC is constructed of SJTW cord available in 14/2 & 12/3 construction in lengths of 50ft -100ft. Listed for hard usage / outdoor usage. 100ft standard includes cages & molded 15A straight blade plug & connector. Compact design packaging for less warehouse space & easy job site clean up.

**All Yellow "High Visable" Unit**

Hard Usage



**Snap Lock Cage**

Bergens unique "snap lock" cage design eliminates those annoying screws & saves time, money & hassle during installation. Bergen's Contractor Grade Series was truly made with the Contractor in mind!!



### 15A Male & Female Ends



### Copper Screw Shell Socket

For better conection & smoother application



### Low Profile Molding Design

Unlike competitors, Bergen's mold design allows all units to be compatible with CFL medium base lamps

### Full Color Packaging



**Designed For Counter Area Display**

## ORDERING INFORMATION

Cat #	Description	Lamp Style	Case/Wt
GL100-142MPC	14/2 SJTW, 100' w/15A male & female	150w max Type "A"	11
GL50-142MPC	14/2 SJTW, 50' w/15A male & female	150w max Type "A"	6
GL100-123MPC	12/3 SJTW, 100' w/15A male & female	150w max Type "A"	18
GL50-123MPC	12/3 SJTW, 50' w/15A male & female	150w max Type "A"	9



www.bergeninc.com

p.800.875.1846

f.800.875.9419




# U.S. Made Temp Light Stringer's

Indoor / Outdoor Use

**Bergen's Deluxe (GL Series)** is an indoor / outdoor Hard Usage, temp light system. Available in 14/2 (black), & 12/2 (yellow) construction each unit is constructed of heavy duty SJTW round cord. The GL series is OSHA & NEC compliant. Lampholders are spaced on 10ft centers & rated for 150 watts. Each unit is supplied with yellow plastic bulb protectors

## Custom Units Available

Because we still manufacture in the U.S., Bergen is capable of making custom lengths & spacing for unique stringer applications. All Black 14/2 or Yellow 12/2 STW units available with minimum of 12" spacing between sockets. Commonly used for restaurant patios, outdoor festivals to small work areas, think of Bergen for all your custom stringer needs.



Available with Metal Guards  
Cat# **MC-200B** 50/carton  
Cat# **MC-200Y** 50/carton  
Cat# **SG-200** 50/carton



# DELUXE SERIES





# YFW-100

## Economy Temporary Lighting Unit

Indoor / Outdoor Use

**Bergens YFW-100** is a basic "Flat" wire unit, manufactured with 14AWG stranded "AWM" flat cord style wire and a pin type lamp-holder every 10ft on center. O.S.H.A. and N.E.C. compliant, each unit is rated for damp locations & contains 10 "Heavy Duty" heat resistant yellow bulb protectors which are uniquely designed for superior performance and extended life. *Available in 14/2 construction, 50'-200'*

### ORDERING INFORMATION

Cat #	Description	Lamp Style	Case/Wt
YFW-100	14/2 AWM, 100' Lampholders 10ft on center	150w max Type "A"	10
YFW-100-20	14/2 AWM, 100' Lampholders 20ft on center	150w max Type "A"	9
YFW-200-20	14/2 AWM, 200' Lampholders 20ft on center	150w max Type "A"	15



**LIGHT-DUTY STRINGER**



# REPLACEMENT CAGES



**Cat# BC-200**  
**"Standard Cage"**

High strength, impact-resistant thermoplastic. Fits most Temporary Light's & lampholders. New "Snap Locking" Collar 150 watt max type "A" bulb.

Packaged 100 per carton



**Cat# EC-200**  
**"Keyless Cage"**

Impact-resistant thermoplastic Adjustable collar. Fits ceiling "Keyless" lampholders, pigtail lampholders, sign & scoreboard lampholders. Screws included 200 watt max type "A" bulb


Packaged 30 per carton



**Cat# SG-200**  
**"Small Wire Guard"**

Keyless Lamp Guard Easy "open-close" bottom for re-lamping. Fits most Temp Light and keyless sockets. Rust resistant zinc plating. Screw's and nuts included. 200 watt max type "A" bulb

Packaged 50 per carton



**Cat# IC-200**  
**"Import Cage"**

High strength, impact-resistant thermoplastic. Fits Model MPC Series Temp Light Stringers. New Zip Tie "Snap Locking" Collar wont fall off the socket! 150 watt max type "A" bulb

Packaged 50 per carton



**Cat# MC-200B**  
**"Metal Cage"**

Heavy duty 10-guage **Black** Vinyl coated Bronze plated 1 1/2" universal collar fits most Temp Light and keyless sockets. Rust resistant zinc plating (*screws included*) Open bottom for easy re-lamping 200 watt max type "A" bulb

Packaged 50 per carton



**Cat# MC-200Y**  
**"Metal Cage"**

Heavy duty 10-guage **Yellow** Vinyl coated Bronze plated 1-1/2" universal collar fits most Temp Light and keyless sockets. Rust resistant zinc plating (*screws included*) Open bottom for easy re-lamping. 200 watt max type "A" bulb

Packaged 50 per carton





LAMP HOLDERS



BK1

### Porcelain Keyless Lampholder

- UL E26 Porcelain Lampholder
- 4-Terminal
- Medium Base fits 3.25" or 4" Outlet Box
- Residential, Commercial & Industrial Use
- Nickel Plated Brass Screwshell
- Stainless Steel Mounting Screws Included

Ordering Information

Cat#	Description	Lamp	Ship Case	WT / Case
BK1	Porcelain Keyless Lamp Holder	Med	50	32
BK2	Plastic Keyless Lamp Holder	Med	108	24



BK2

### Plastic Keyless Lampholder

- UL E309529
- 4-Terminal
- Medium Base fits 3.25" or 4" Outlet Box
- Residential, Commercial & Industrial Use
- Aluminum Screwshell
- Stainless Steel Mounting Screws Included
- UV Resistant will not fade or discolor

Ordering Information

Cat#	Description	Base	Max Wattage	Ship Case	WT / Case
LH-22WP	US Made Pigtail Lampholder With Hook	Medium	200	100	11
LH-145WP	Pigtail Lampholder No Hook	Medium	200	100	11
521-WP	Pin-Type Socket Meets U.L. 496 Requirements	Medium	200	100	11





# Flexible Steel Pre-Assembled Whips

Fixture Whips - Die Cast Screw In Connectors or Snap-in Fittings for easy hook-ups


- U.L. File Number: E361306 , E361307
- Stranded or Solid Conductors
- Meets Requirements of 2011 NEC
- 25pc Bundle or 200pc Barrel

## Ordering Info

Cat#	Type	Description	Bundle	Barrel
BFW-1236-01	Steel	Fixture Whip, 6ft, 12awg Stranded 3 Wire, Steel FMC, Blk/Wht/Grn, <i>Screw-In Connector</i>	25	200
BFW-1436-01	Steel	Fixture Whip, 6ft, 14awg Stranded 3 Wire, Steel FMC, Blk/Wht/Grn, <i>Screw-In Connector</i>	25	200
BFW-1236S-01	Steel	Fixture Whip, 6ft, 12awg Solid 3 Wire, Steel FMC, Blk/Wht/Grn, <i>Screw-In Connector</i>	25	200
BFW-1236S	Steel	Fixture Whip, 6ft, 12awg Solid 3 Wire, Steel FMC, Blk/Wht/Grn, <i>Snap-In Connector</i>	25	200

**Steel or Aluminum, Custom lengths , Ends & Wire Colors. Call Bergen for a complete list.**

Ordering System



**FIXTURE WHIPS**





**HEAVY  
DUTY**

**OUTDOOR CORDS**

## **OC50123LT - 50ft. 12/3 SJTW Yellow Extension Cord**

### **Features**

- Water Resistant
- Flame Retardant
- Ultra Flexible
- Corrosion Resist Blades
- Lighted Ends

### **Specifications**

- **Length (ft):** 50
- **Color:** Yellow
- **Gauge:** 12/3
- **Wire Type:** SJTW
- **Certifications:** UL or equivalent
- **Electrical Ratings:** 15A/ 125V/ 1875W
- **Product Packaging:** Sleeve
- **Unit Measurement (DxWxH):** 2.5x7.5x15
- **Unit Weight (lbs):** 7.65
- **Master Carton Type:** Brown Box
- **Master Carton Measurements:** 16x13.75x8.25
- **Master Carton Weight (lbs):** 47.4
- **Master Carton Qty:** 6

**Unit UPC:** 752560 660094  
**Master Carton UPC:** 30752560 660095



## **OC100123LT - 100ft. 12/3 SJTW Yellow Extension Cord**

### **Features**

- Water Resistant
- Flame Retardant
- Ultra Flexible
- Corrosion Resist Blades
- Lighted Ends

### **Specifications**

- **Length (ft):** 100
- **Color:** Yellow
- **Gauge:** 12/3
- **Wire Type:** SJTW
- **Certifications:** UL or equivalent
- **Electrical Ratings:** 15A/ 125V/ 1625W
- **Product Packaging:** Sleeve
- **Unit Measurement (DxWxH):** 3x9x15.5
- **Unit Weight (lbs):** 14.5
- **Master Carton Type:** Brown Box
- **Master Carton Measurements:** 18.25x17.3x6.75
- **Master Carton Weight (lbs):** 60.6
- **Master Carton Qty:** 4

**Unit UPC:** 752560 660100  
**Master Carton UPC:** 30752560 660101





**HEAVY  
DUTY**

## **OC50143 - 50ft. 14/3 SJTW Orange Extension Cord**

### **Features**

- Water Resistant
- Flame Retardant
- Ultra Flexible
- Corrosion Resist Blades

### **Specifications**

- **Length (ft):** 50
- **Color:** Orange
- **Gauge:** 14/3
- **Wire Type:** SJTW
- **Certifications:** UL or equivalent
- **Electrical Ratings:** 15A/ 125V/ 1875W
- **Product Packaging:** Sleeve
- **Unit Measurement (DxWxH):** 2x6.5x14.5
- **Unit Weight (lbs):** 4.75
- **Master Carton Type:** Brown Box
- **Master Carton Measurements:** 13.75x13.75x10
- **Master Carton Weight (lbs):** 39.5
- **Master Carton Qty:** 8

**Unit UPC:** 752560 660063

**Master Carton UPC:** 30752560 660064



## **OC100143 - 100ft. 14/3 SJTW Orange Extension Cord**

### **Features**

- Water Resistant
- Flame Retardant
- Ultra Flexible
- Corrosion Resist Blades

### **Specifications**

- **Length (ft):** 100
- **Color:** Orange
- **Gauge:** 14/3
- **Wire Type:** SJTW
- **Certifications:** UL or equivalent
- **Electrical Ratings:** 13A/ 125V/ 1625W
- **Product Packaging:** Sleeve
- **Unit Measurement (DxWxH):** 2.8x9.2x14.2
- **Unit Weight (lbs):** 9.75
- **Master Carton Type:** Brown Box
- **Master Carton Measurements:** 17x16.5x6.5
- **Master Carton Weight (lbs):** 39.2
- **Master Carton Qty:** 4

**Unit UPC:** 752560 660070

**Master Carton UPC:** 30752560 660071



**OUTDOOR CORDS**

[www.bergeninc.com](http://www.bergeninc.com)

p.800.875.1846

f.800.875.9419



## D100304 - 4ft. 10/3 SRDT Gray 30Amp Dryer Cord

### Features

- Cord includes strain relief kit
- 3-wire cord fits more homes built prior to 1996
- Ring terminals for secure connection



### Specifications

Length (ft):	4
Color:	Gray
Gauge:	10/3
Wire Type:	SRDT
Certification:	UL or equivalent
Product Packaging:	Sleeve
Unit Measurements (DxWxH):	0.90 x 3.10 x 13.00
Unit Weight (lbs):	1.12
Master Carton Type:	Bin-Box
Master Carton Measurements (DxWxH):	14.43 x 7.24 x 7.37
Master Carton Weight (lbs):	12.51
Master Carton Pack Quantity:	10
Master Carton Cube (cu. ft.):	0.45

Unit UPC: 752560 880010  
Master Carton UPC: 50752560 880015

## D100306 - 6ft. 10/3 SRDT Gray 30Amp Dryer Cord

### Features

- Cord includes strain relief kit
- 3-wire cord fits more homes built prior to 1996
- Ring terminals for secure connection



### Specifications

Length (ft):	6
Color:	Gray
Gauge:	10/3
Wire Type:	SRDT
Certification:	UL or equivalent
Product Packaging:	Sleeve
Unit Measurements (DxWxH):	1.15 x 3.50 x 13.00
Unit Weight (lbs):	1.51
Master Carton Type:	Bin-Box
Master Carton Measurements (DxWxH):	14.43 x 8.04 x 7.37
Master Carton Weight (lbs):	15.61
Master Carton Pack Quantity:	10
Master Carton Cube (cu. ft.):	0.49

Unit UPC: 752560 880027  
Master Carton UPC: 50752560 880022

DRYER CORDS 3-WIRE





# DRYER CORDS 4-WIRE

## D100404 - 4ft. 10/4 SRDT Black 30Amp Dryer Cord

### Features

- Cord includes strain relief kit
- 4-wire cord fits most homes built after 1996
- Ring terminals for secure connection



### Specifications

Length (ft):	4
Color:	Black
Gauge:	10/4
Wire Type:	SRDT
Certification:	UL or equivalent
Product Packaging:	Sleeve
Unit Measurements (DxWxH):	1.50 x 5.00 x 13.00
Unit Weight (lbs):	1.58
Master Carton Type:	Bin-Box
Master Carton Measurements (DxWxH):	14.43 x 11.04 x 8.92
Master Carton Weight (lbs):	17.83
Master Carton Pack Quantity:	10
Master Carton Cube (cu. ft.):	0.82

Unit UPC: 752560 880034

Master Carton UPC: 50752560 880039

## D100405 - 5ft. 10/4 SRDT Black 30Amp Dryer Cord

### Features

- Cord includes strain relief kit
- 4-wire cord fits most homes built after 1996
- Ring terminals for secure connection



### Specifications

Length (ft):	5
Color:	Black
Gauge:	10/4
Wire Type:	SRDT
Certification:	UL or equivalent
Product Packaging:	Sleeve
Unit Measurements (DxWxH):	1.50 x 5.00 x 13.00
Unit Weight (lbs):	1.83
Master Carton Type:	Bin-Box
Master Carton Measurements (DxWxH):	14.43 x 8.40 x 10.65
Master Carton Weight (lbs):	16.51
Master Carton Pack Quantity:	8
Master Carton Cube (cu. ft.):	0.75

Unit UPC: 752560 880041

Master Carton UPC: 50752560 880046

## D100406 - 6ft. 10/4 SRDT Black 30Amp Dryer Cord

### Features

- Cord includes strain relief kit
- 4-wire cord fits most homes built after 1996
- Ring terminals for secure connection



### Specifications

Length (ft):	6
Color:	Black
Gauge:	10/4
Wire Type:	SRDT
Certification:	UL or equivalent
Product Packaging:	Sleeve
Unit Measurements (DxWxH):	1.50 x 5.00 x 13.00
Unit Weight (lbs):	2.24
Master Carton Type:	Bin-Box
Master Carton Measurements (DxWxH):	14.43 x 6.04 x 10.10
Master Carton Weight (lbs):	14.89
Master Carton Pack Quantity:	6
Master Carton Cube (cu. ft.):	0.51

Unit UPC: 752560 880058

Master Carton UPC: 50752560 880053





## R628104 - 4ft. 6/2 & 8/1 SRDT Gray 50Amp Range Cord

### Features

- Cord includes strain relief kit
- 3-wire cord fits more homes built prior to 1996
- Ring terminals for secure connection



### Specifications

<b>Length (ft):</b>	4
<b>Color:</b>	Gray
<b>Gauge:</b>	6/2 & 8/1
<b>Wire Type:</b>	SRDT
<b>Certification:</b>	UL or equivalent
<b>Product Packaging:</b>	Sleeve
<b>Unit Measurements (DxWxH):</b>	1.30 x 3.90 x 13.00
<b>Unit Weight (lbs):</b>	1.81
<b>Master Carton Type:</b>	Brown-Box
<b>Master Carton Measurements (DxWxH):</b>	14.43 x 8.84 x 7.37
<b>Master Carton Weight (lbs):</b>	19.61
<b>Master Carton Pack Quantity:</b>	10
<b>Master Carton Cube (cu. ft.):</b>	0.54

Unit UPC: 752560 881000  
Master Carton UPC: 50752560 881005

## R628106 - 6ft. 6/2 & 8/1 SRDT Gray 50Amp Range Cord

### Features

- Cord includes strain relief kit
- 3-wire cord fits more homes built prior to 1996
- Ring terminals for secure connection



### Specifications

<b>Length (ft):</b>	6
<b>Color:</b>	Gray
<b>Gauge:</b>	6/2 & 8/1
<b>Wire Type:</b>	SRDT
<b>Certification:</b>	UL or equivalent
<b>Product Packaging:</b>	Sleeve
<b>Unit Measurements (DxWxH):</b>	1.00 x 5.75 x 12.00
<b>Unit Weight (lbs):</b>	2.51
<b>Master Carton Type:</b>	Brown-Box
<b>Master Carton Measurements (DxWxH):</b>	13.43 x 8.89 x 9.05
<b>Master Carton Weight (lbs):</b>	21.75
<b>Master Carton Pack Quantity:</b>	8
<b>Master Carton Cube (cu. ft.):</b>	0.63

Unit UPC: 752560 881017  
Master Carton UPC: 50752560 881012

RANGE CORDS 3-WIRE



## R628204 - 4ft. 6/2 & 8/2 SRDT Black 50Amp Range Cord

### Features

- Cord includes strain relief kit
- 4-wire cord fits most homes built after 1996
- Ring terminals for secure connection



### Specifications

Length (ft):	4
Color:	Black
Gauge:	6/2 & 8/2
Wire Type:	SRDT
Certification:	UL or equivalent
Product Packaging:	Sleeve
Unit Measurements (DxWxH):	1.75 x 5.00 x 13.00
Unit Weight (lbs):	2.36
Master Carton Type:	Brown-Box
Master Carton Measurements (DxWxH):	14.43 x 8.40 x 11.27
Master Carton Weight (lbs):	20.82
Master Carton Pack Quantity:	8
Master Carton Cube (cu. ft.):	0.79

Unit UPC: 752560 881024  
 Master Carton UPC: 50752560 881029

## R628205 - 5ft. 6/2 & 8/2 SRDT Black 50Amp Range Cord

### Features

- Cord includes strain relief kit
- 4-wire cord fits most homes built after 1996
- Ring terminals for secure connection



### Specifications

Length (ft):	5
Color:	Black
Gauge:	6/2 & 8/2
Wire Type:	SRDT
Certification:	UL or equivalent
Product Packaging:	Sleeve
Unit Measurements (DxWxH):	1.75 x 5.00 x 13.00
Unit Weight (lbs):	2.89
Master Carton Type:	Brown-Box
Master Carton Measurements (DxWxH):	14.43 x 6.04 x 11.27
Master Carton Weight (lbs):	18.91
Master Carton Pack Quantity:	6
Master Carton Cube (cu. ft.):	0.57

Unit UPC: 752560 881031  
 Master Carton UPC: 50752560 881036

RANGE CORDS 4-WIRE



# GARBAGE DISPOSAL CORDS



**PS16303R - 3ft. 16/3 SPT-3 Gray Garbage Disposal Cord w/ Right Angle Plug**

### Features

- 13A/ 125V/ 1625W
- 3 Conductor SPT-3 Wire
- Right Angle U-Ground Plug

**Unit UPC:** 752560 882007  
**Master Carton UPC:** 50752560 882002

### Specifications

- Length (ft): 3
- Color: Gray
- Gauge: 16/3
- Wire Type: SPT-3
- Certifications: UL or equivalent
- Product Packaging: Sleeve
- Master Carton Pack Quantity: 60
- Master Carton Weight: 16.06lbs
- Master Carton Measurement: 14.75x9.5x7.5



**PS16306R - 6ft. 16/3 SPT-3 Gray Garbage Disposal Cord w/ Right Angle Plug**

### Features

- 13A/ 125V/ 1625W
- 3 Conductor SPT-3 Wire
- Right Angle U-Ground Plug

**Unit UPC:** 752560 882021  
**Master Carton UPC:** 50752560 882026

### Specifications

- Length (ft): 6
- Color: Gray
- Gauge: 16/3
- Wire Type: SPT-3
- Certifications: UL or equivalent
- Product Packaging: Sleeve
- Master Carton Pack Quantity: 40
- Master Carton Weight: 18.70lbs
- Master Carton Measurement: 14.75x10.5x7.1



**PS16303 - 3ft. 16/3 SPT-3 Gray Garbage Disposal Cord w/ Straight Plug**

### Features

- 13A/ 125V/ 1625W
- 3 Conductor SPT-3 Wire
- U-Ground Plug

**Unit UPC:** 752560 882014  
**Master Carton UPC:** 50752560 882019

### Specifications

- Length (ft): 3
- Color: Gray
- Gauge: 16/3
- Wire Type: SPT-3
- Certifications: UL or equivalent
- Product Packaging: Sleeve
- Master Carton Pack Quantity: 60
- Master Carton Weight: 15.73lbs
- Master Carton Measurement: 14.75x9.5x7.5



**PS16306 - 6ft. 16/3 SPT-3 Gray Garbage Disposal Cord w/ Straight Plug**

### Features

- 13A/ 125V/ 1625W
- 3 Conductor SPT-3 Wire
- U-Ground Plug

**Unit UPC:** 752560 882038  
**Master Carton UPC:** 50752560 882033

### Specifications

- Length (ft): 6
- Color: Gray
- Gauge: 16/3
- Wire Type: SPT-3
- Certifications: UL or equivalent
- Product Packaging: Sleeve
- Master Carton Pack Quantity: 40
- Master Carton Weight: 18.48lbs
- Master Carton Measurement: 14.75x10.5x6.75



Bergen has an extensive line of Tube Guards including standard tubes for everyday use to special UV filtering, Matrix, T5 & light changing color tubes. Made in the USA since 1973, Bergen is your one stop shop for all Tube Guards & accessories.



# FG SERIES

FOR ALL YOUR TUBE GUARD NEEDS

## STANDARD TUBES

- T5, T6, T8 & T12
- Food Preparation Areas
- Public Use Areas
- Commercial Kitchens



## COLORS

A quick low cost way to change the color of any room or area to create atmosphere



## MATRIX

Glare Reducer

- Dims lamp output
- Creates a smoother, softer light
- Eliminates hot spots in fixture



## ACCESSORY

Lamp Lock



## UV Filtering




UV filtering tubes eliminate virtually all UV radiation (over 99%) and thereby retard photochemical degradation in textiles, water colors, historical documents, works of art & other sensitive display items. These UV Tube Guards are used in museums, art galleries, libraries, classrooms & other areas where the prevention of UV degradation is critical.

CLEAR - 390nm



AMBER - 540nm



RED - 600nm



# TUBE GUARDS

[www.bergeninc.com](http://www.bergeninc.com)

p.800.875.1846


f.800.875.9419





## Prismatic P12 Lens

The basic industry standard. This panel offers an economical compromise for non-specification lighting needs. Female conical combines performance, appearance and economy. Best value & excellent strength to weight ratio. Typical use for P12 prismatic diffuser range from Office, Schools, Clinics & Retail areas. The P12 pattern offers maximum efficiency and good brightness control in direct glare.



Prismatic Lens		
Catalog No.	Description	
B-9300	22.5" x 46.5" .095 Acrylic P12	30/Case
B-9246	23.75" x 47.75" .095 Acrylic P12	30/Case
B-9114	23.75" x 47.75" .125 Acrylic P12	25/Case

\*\* Other sizes available. Please contact Bergen for additional information

## JC SERIES

FOR ALL YOUR VAPORTIGHT NEEDS

IP65/IP67



## Vapor Tight Enclosures

### Approvals and/or Listings

Underwriters Laboratories  
NSF International  
U.S. Department of Agriculture  
Canadian Standards Association

### Applications

Food Processing Facilities  
Kitchens  
Parking Garages  
Car Washes  
Schools & Public Facilities

Complete Units	
Catalog No.	Description
JC 220-CU	2' Shallow Housing, High Impact Acrylic/DR Diffuser, Latches & End Plugs
JC 248-CU	4' Deep Housing, High Impact Acrylic/DR Diffuser, Latches & End Plugs
JC 296-CU	8' Deep Housing, High Impact Acrylic/DR Diffuser, Latches & End Plugs
Replacement Diffusers	
Catalog No.	Description
JC 240-L	4' Shallow High Impact Acrylic/DR Clear Crepe Diffuser
JC 248-L	4' Deep High Impact Acrylic/DR Clear Crepe Diffuser
JC 296-L	8' Deep High Impact Acrylic/DR Clear Crepe Diffuser