



KICHLER.

WELCOME

The stars and moon may bring subtle light to the night sky – but the true beauty in outdoor lighting is often a bit closer to home.

From your front door to your back patio and beyond, Decorative Outdoor Lighting from Kichler helps enhance your home in ways that match your own personal style. At night, they make your guests feel welcome. During the day, they add style and character to your abode. Step outside, and you'll discover a range of stylish collections, each designed with inspiring finishes, fresh details and unequalled quality. You'll find everything you need, including post lanterns, outdoor wall lights, ceiling lights, ceiling fans, pendants – even chandeliers. And our offering is designed to illuminate a variety of exterior locations with coordinated ease, so you can carry the look you love to your entryway, driveway, pathways, decks, entertaining areas and more.

Your home. Hundreds of different Kichler ways to bring it to light.





TABLE OF CONTENTS

- 5 Contents by Collection Name
- 6 Visual Index
- 18 Outdoor LED
- 42 Outdoor Living
- 188 Accessories
- 190 Light Bulb Reference
- 192 Index
- 195 Legend



Become a fan of Kichler Lighting at:
[facebook.com](https://www.facebook.com/kichlerlighting), search Kichler Lighting



Follow us on twitter at:
twitter.com/kichlerlight



Find us on Pinterest at:
<http://pinterest.com/kichlerstyle/>




Join us on Houzz at:
<http://www.houzz.com/pro/kichlerlighting/kichler>



Watch us on
[youtube.com/KichlerLighting](https://www.youtube.com/KichlerLighting)

OUTDOOR LIGHTING



DESIGNS CRAFTED TO INSPIRE

Kichler is known for setting lighting design trends with popular finishes, fashion-forward collections and handcrafted details. We take great pride in the craftsmanship that we build into everything we create. The result is a collection of distinctive outdoor products that help express your unique style, taste and personality - whether it be casual, contemporary or traditional. We take pride in transforming light into beautiful, functional works of art that inspire you.

TIME TO ENLIGHTEN

WHY CHOOSE KICHLER OUTDOOR LIGHTING

1

ENHANCE YOUR HOME'S BEAUTY

The warm welcoming glow of Kichler Outdoor Lighting can instantly improve your home's curb appeal. With the right fixture, you can add drama while highlighting the unique architectural details of your home.



2

INCREASE YOUR FAMILY'S SAFETY & SECURITY

Poorly lit spaces are a concern for everyone. They can increase the likelihood of accidents or theft. Kichler Outdoor Lighting adds visibility, allowing you, your family and your friends to move around more safely and easily after dark.

3

CREATE A LIVABLE OUTDOOR SPACE

Outdoor living is one of today's fastest-growing trends, and beautiful outdoor lighting is key in extending your outdoor space's charm and functionality long after sunset. Extend your interior space outside and bring warmth to any outdoor area.



4

ADD VALUE TO YOUR HOME

Kichler Outdoor Lighting can easily distinguish your home from others in a competitive real estate market. As a result of premium lighting choices, your property is likely to be perceived as having greater everyday and long-term value. And that means money.



KICHLER LED LIGHTING

EXCEEDS THE STANDARDS FOR RELIABILITY AND BEAUTY.

SYMBOL GUIDE



-  UL DAMP
-  UL WET
-  Dark Sky Compliant
-  ADA Compliant
American Disabilities Act
-  LED
Light Emitting Diodes
-  Hybrid Outdoor
-  Energy Star
-  FCC
Federal Communications Commission.
Devices with this logo comply with part 15 of the FCC rules.
-  California Title 24 Compliant
-  Lamp Included
-  Installation Instructions:
Fixture must be supported independently of the outlet box unless the outlet box is UL listed for the weight to be supported. Consult a qualified electrician / installer. Required installation parts included.
-  Fixture requires supply wire rated for at least 90° C.
-  Fixture requires supply wire rated for at least 75° C.
-  When electrical connection is made inside the fixture, supply wire must be rated at least 75° C. When electrical connection is made in an outlet box, supply wire must be rated at least 60° C.

TABLE OF CONTENTS

LIGHTING COLLECTIONS

Address Light	186	Mount Vernon EE	136
Alameda™	96-99	Mount Vernon LED	32
Amber Valley™ LED	26	Newport™	40
Ashland Bay	70	New Street™	182
Atwood	67	Northview	114
Barrie	178	Outdoor Wall	38
Bay Shore™	149	Outdoor Chandeliers	44
Bowen™	68	Outdoor Ceiling	183
Bradford	110	Outdoor Wall EE	184
Bridge Point	84	Pacific Edge™	62-64
Brive™ LED	27	Pallerton Way™	118
Camden™	56	Park Row	122
Cameron™	102	Pebble Lane	86
Caterham™	92	Portman Square™	104
Celino™	40	Ripley™	83
Cesya™ LED	28	Rustic™	78
Chesapeake™	170-172	Salisbury™	142-145
Cidney™ LED	27	Sausalito™	146
Clear Point	76	Savannah Estates™	166
Courtyard™	138-141	Seaside™	82
Courtyard™ EE	137	Sedo™ LED	30
Cross Creek™	106	Shelby LED	33
Dahlia LED	18	Sorel™ LED	24
Eau Claire™	167	Soria™	100
Embassy Row	173	South Hope™	54
Estella LED	21	Stonebrook	94
Franceasi™	60	Sumner Court	90
Franceasi™ LED	35	Tolerand™	164
Galemore	116	Tournai™	124-131
Grove Mill™	148	Town Light	107
Halleron™	111	Townhouse™	176
Hanford™	77	Tremillo™	58
Harbor Row	112	Turlee™	168
Harvest Ridge	72	Venetian Rain™	160-163
Hatteras Bay™	74	Walden LED	36
Hatteras Bay™ LED	33	Wesley LED	19
Hayman Bay™	120	Westington™	80
Kirkwood™	174	Wiscombe Park™	154-159
Lantana™	66	Woodhollow Lane	88
LED Wall	37	Zolder	41
Lyndon™	48-53		
Madison	181	OUTDOOR	16
Madison EE	180	OUTDOOR LIVING	42
Magnolia LED	20	DARK SKY ACCESSORIES	185
Manningham™	150-153	POST ACCESSORIES	188
Margeaux LED	22	BULB & LAMP REFERENCE	190
Maya Palm™ LED	34	INDEX	192
McAdams™	65	LEGEND	195
Morris™	108		
Mount Vernon	132-135		

LED VISUAL INDEX



Amber Valley™ LED
26



Brive™ LED
27



Cesya™ LED
28



Cidney™ LED
27



Dahlia LED
18



Estella LED
21



Franceasi™ LED
35



Hatteras Bay™ LED
33



LED Wall
37



Magnolia LED
20



Margeaux LED
22



Maya Palm™ LED
34



Mount Vernon LED
32



Sedo™ LED
30



Sorel™ LED
24



Walden LED
36



Wesley LED
19

OUTDOOR LIGHTING VISUAL INDEX



Address Light
186



Alameda™
96



Ashland Bay
70



Atwood
67



Barrie
178



Bay Shore™
149



Bowen™
68



Bradford
110



Bridge Point
84



Camden™
56



Cameron™
102



Caterham™
92



Celino™
40



Chesapeake™
170



Clear Point
76



Courtyard™
138



Cross Creek™
106



Eau Claire™
167



Embassy Row
173



Franceasi™
60



Galemore
116



Grove Mill™
148



Halleron™
111



Hanford
77

OUTDOOR LIGHTING VISUAL INDEX



Harbor Row™
112



Harvest Ridge
72



Hatteras Bay™
74



Hayman Bay™
120



Kirkwood™
174



Lantana™
66



Lyndon™
48



Madison
181



Manningham™
150



McAdams™
65



Morris™
108



Mount Vernon
132



Newport™
40



New Street™
182



Northview
114



Outdoor Wall
38



Outdoor Ceiling
183



Outdoor Chandeliers
44



Pacific Edge™
62



Pallerton Way™
118



Park Row
122



Pebble Lane
86



Portman Square™
104



Ripley™
83



Rustic™
78



Salisbury™
142



Sausalito™
146



Savannah Estates™
166



Seaside™
82



Soria™
100



South Hope™
54



Stonebrook
94



Sumner Court
90



Tolerand™
164



Tournai™
124



Town Light
107



Townhouse™
176



Tremillo™
58



Turlee™
168



Venetian Rain™
160



Westington™
80



Wiscombe Park™
154



Woodhollow Lane
88



Zolder
41

ENERGY EFFICIENT VISUAL INDEX



Alameda™
96



Atwood
67



Camden™
56



Cameron™
102



Outdoor Ceiling
183



Courtyard™
137



Lantana™
66



Madison
180



McAdams™
65



Mount Vernon
136



Newport™
40



Outdoor Wall
184



Pacific Edge™
62



Salisbury™
142



Seaside™
82



Tremillo™
58

ENERGY STAR



Kichler Lighting has been a proud sponsor of the Energy Star Program since 2002. In conjunction with the new Energy Star V2.0 standard, we are making improvements to our assortment of

qualified products. As they are qualified, Energy Star will post them to their website. Please consult the Energy Star website at www.energystar.gov for our current assortment of qualified products, in addition to Kichler.com.

LANDSCAPE LIGHTING OVERVIEW

PATH & SPREAD



15429
Cathedral
Path Light
TZT



15322
Cross Creek
Lantern Path Light
AGZ



15438
Traditional Marine
Lantern Path Light
OB, OZ

ACCENT LIGHT



16000-16005
12V Single LED Accent Light
AZT, BBR, BKT, WHT



15384
Mini Accent Light
AZT, BKT, CBR, CO



15861R
LED Wall Wash Accent Light
AZT, BBR, BKT

DECK & PATIO



16111
Four Corner Deck Light
AZT, BKT, TZT




16112
Overlay Deck Light
AZT



16113
Perforated Deck Light
AZT, CO, TZT

Kichler Landscape Lighting Catalog K215

View our entire line of landscape
lighting at kichler.com/landscape
or request a catalog.



DECORATIVE LIGHTING OVERVIEW

CHANDELIERS



Piper
43723 ESP



Passport
43760 NI



Rosalie
43805 SGD

PENDANTS



Vance
43933 NBR



City Loft™
43783 PN



Cobson™
42649 OZ

BATH



Millwright™
45544 DAG



Braelyn™
45459 CH



Trinsic™
45657 CHLED

WALL SCONCES



Mona
43375 NBR



LED
42372 NILED



KICHLER

Kichler Interior Sourcebook
Catalog K116



BRING THE BEAUTY INDOORS! Our comprehensive offering includes hundreds of interior ceiling fixtures, chandeliers, bath lights, sconces, ceiling fans, pendants and more. Ask for your Kichler Sourcebook today or view it online at kichler.com.



CEILING FAN CATALOG K416 Kichler offers inspiring designs, finishes and details throughout our entire collection of ceiling fans. To view our extensive offering, visit kichler.com or request our Ceiling Fan Collections catalog K416.



LIGHTING SYSTEMS CATALOG For a residential kitchen or bath...home office... new restaurant...or a unique boutique... Kichler Lighting Systems can highlight the finest features. Visit kichler.com to see our Cabinet Lighting/Lighting Systems supplements and catalogs.

OUTDOOR

STYLE & SAFETY

Buzzwords abound when it comes to the beauty of your home's exterior. Curb appeal. Architectural interest. And let's not forget "location, location, location." Because, after all, there are so many places you can put style -- and so many ways it can make your home beautiful and more functional at night. Our distinctive offering illuminates all those important locations with coordinated ease: entryways, driveways, pathways, decks, dining areas and more. And with more light comes more reasons to head outside -- extending the function of your outdoor spaces well after dark.





DAHLIA LED

ARCHITECTURAL BRONZE™ FINISH
WITH WHITE GLASS



These devices
comply with part 15
of the FCC Regulations.

LED OUTPUT

49557 AZLED	1800 LUMENS*, 40 WATTS, 3000 KELVIN, CRI 90, 40K LIFE
49558 AZLED	2400 LUMENS*, 60 WATTS, 3000 KELVIN, CRI 90, 40K LIFE

*Initial Lumens. Visit kichler.com for recent performance and certification data.



A | **49557 AZLED**
Indoor/Outdoor Wall
ADA Compliant



B | **49558 AZLED**
Large Indoor/Outdoor Wall
ADA Compliant

ALUMINUM
CONSTRUCTION

DAHLIA LED

	LED ITEM #	FINISH	LIGHT SOURCE	W	H	EXT.	NOTES
A	49557 AZLED	AZ	(2) 40W	8	18.75	4	Dimmable.
B	49558 AZLED	AZ	(2) 60W	8	25.25	4	Dimmable.

Measurements shown in inches. U.S. & Canada Patent Pending.

WESLEY LED

PLATINUM OR TEXTURED ARCHITECTURAL
BRONZE™ FINISH



A | **49278 PLED**
Indoor/Outdoor Wall
ADA Compliant



A | **49278 AZTLED**
Indoor/Outdoor Wall
ADA Compliant



B | **49279 PLED**
Indoor/Outdoor Wall
ADA Compliant



Clear Glass on Top
to Provide Up Light

B | **49279 AZTLED**
Indoor/Outdoor Wall
ADA Compliant



These devices
comply with part 15
of the FCC Regulations.

LED OUTPUT

49278 AZTLED/PLED	720 LUMENS*, 10 WATTS, 3000 KELVIN, CRI 90, 40K LIFE
49279 AZTLED/PLED	1440 LUMENS*, 20 WATTS, 3000 KELVIN, CRI 90, 40K LIFE

*Initial Lumens. Visit kichler.com for recent performance and certification data.

WESLEY LED

ALUMINUM
CONSTRUCTION

	LED ITEM #	FINISH	LIGHT SOURCE	W	H	EXT.	HCWO	NOTES
A	49278 AZTLED / 49278 PLED	AZT, PL	10W	7	7.5	4	3.75	Dimmable.
B	49279 AZTLED / 49279 PLED	AZT, PL	(2) 20W	7	14	4	7	Dimmable.

Measurements shown in inches. U.S. & Canada Patent Pending.



MAGNOLIA LED

OLDE BRONZE® FINISH WITH
SATIN ETCHED CASED OPAL GLASS



A | **49605 OZLED**
Indoor/Outdoor Wall
ADA Compliant



B | **49606 OZLED**
Indoor/Outdoor Wall
ADA Compliant



These devices
comply with part 15
of the FCC Regulations.

LED OUTPUT

49605 AZTLED	1800 LUMENS*, 40 WATTS, 3000 KELVIN, CRI 90, 40K LIFE
49606 AZTLED	2400 LUMENS*, 60 WATTS, 3000 KELVIN, CRI 90, 40K LIFE

*Initial Lumens. Visit kichler.com for recent performance and certification data.

MAGNOLIA LED


ALUMINUM
CONSTRUCTION

	LED ITEM #	FINISH	LIGHT SOURCE	W	H	EXT.	NOTES
A	49605 OZLED	OZ	(2) 40W	6	16	4	Dimmable.
B	49606 OZLED	OZ	(2) 60W	8	22	4	Dimmable.

Measurements shown in inches. U.S. & Canada Patent Pending.


ESTELLA LED

TEXTURED ARCHITECTURAL BRONZE™ FINISH



A | **49607 AZTLED**
Indoor/Outdoor Wall

B | **49608 AZTLED**
Indoor/Outdoor Wall



LED OUTPUT

49607 AZTLED	720 LUMENS*, 10 WATTS, 3000 KELVIN, CRI 90, 40K LIFE
49608 AZTLED	1440 LUMENS*, 20 WATTS, 3000 KELVIN, CRI 90, 40K LIFE

*Initial Lumens. Visit kichler.com for recent performance and certification data.

ESTELLA LED

ALUMINUM
CONSTRUCTION

	LED ITEM #	FINISH	LIGHT SOURCE	W	H	EXT.	HCWO	NOTES
A	49607 AZTLED	AZT	10W	6	12	4.25	6	Dimmable.
B	49608 AZTLED	AZT	(2) 20W	6	16.5	4.25	8.25	Dimmable.

Measurements shown in inches. U.S. & Canada Patent Pending.

MARGEAUX LED

BRUSHED ALUMINUM OR OLDE BRONZE®
FINISH WITH SATIN ETCHED GLASS



A | **49538 BALED**
Indoor/Outdoor Wall
ADA Compliant



A | **49538 OZLED**
Indoor/Outdoor Wall
ADA Compliant



These devices
comply with part 15
of the FCC Regulations.

LED OUTPUT

49538 BALED	1200 LUMENS*, 30 WATTS 3000 KELVIN, CRI 90, 40K LIFE
49538 OZLED	1200 LUMENS*, 30 WATTS 3000 KELVIN, CRI 90, 40K LIFE

*Initial Lumens. Visit kichler.com for recent performance and certification data.

MARGEAUX LED

	LED ITEM #	FINISH	LIGHT SOURCE	W	H	EXT.	NOTES
A	49538 BALED / 49538 OZLED	BA, OZ	30W	4.5	12	2.5	Dimmable.

Measurements shown in inches. U.S. & Canada Patent Pending.



B | **49539 BALED**
Indoor/Outdoor Wall
ADA Compliant



B | **49539 OZLED**
Indoor/Outdoor Wall
ADA Compliant

LED OUTPUT

49539 BALED	1600 LUMENS*, 40 WATTS 3000 KELVIN, CRI 90, 40K LIFE
49539 OZLED	1600 LUMENS*, 40 WATTS 3000 KELVIN, CRI 90, 40K LIFE

*Initial Lumens. Visit kichler.com for recent performance and certification data.

CAST ALUMINUM
CONSTRUCTION

MARGEUX LED

	LED ITEM #	FINISH	LIGHT SOURCE	W	H	EXT.	NOTES
B	49539 BALED / 49539 OZLED	BA, OZ	(2) 40W	6	16	3.75	Dimmable.

Measurements shown in inches. U.S. & Canada Patent Pending.



Sorel™ LED Outdoor Wall 49118 AZLED | Page 25

SOREL™ LED

ARCHITECTURAL BRONZE™ FINISH
WITH RIBBED CLEAR GLASS



A | **49117 AZLED**
Outdoor Wall



B | **49118 AZLED**
Outdoor Wall



C | **49190 AZLED**
Outdoor Wall

LED OUTPUT

49117 AZLED	800 LUMENS*, 10 WATTS 3000 KELVIN, CRI 80, 40K LIFE
49118 AZLED	800 LUMENS*, 10 WATTS 3000 KELVIN, CRI 80, 40K LIFE
49190 AZLED	1600 LUMENS*, 20 WATTS 3000 KELVIN, CRI 80, 40K LIFE

*Initial Lumens. Visit kichler.com for recent performance and certification data.

ALUMINUM
CONSTRUCTION

SOREL™ LED

	LED ITEM#	FINISH	LIGHT SOURCE	W	H	EXT.	HCWO	NOTES
A	49117 AZLED	AZ	10W	5.25	10.75	5.5	5.5	Dimmable.
B	49118 AZLED	AZ	10W	6.5	16	5.75	8	Dimmable.
C	49190 AZLED	AZ	(2) 20W	10.75	16	5.75	8	Dimmable.

Measurements shown in inches. U.S. & Canada Patent Pending.

AMBER VALLEY LED

TEXTURED BLACK FINISH WITH
ETCHED SEEDED GLASS



A | **49623 BKTLED**
Outdoor Wall



B | **49622 BKTLED**
Outdoor Wall



C | **49626 BKTLED**
Outdoor Pendant



D | **49624 BKTLED**
Outdoor Wall



E | **49625 BKTLED**
Outdoor Post

LED OUTPUT

49623 BKTLED	1200 LUMENS*, 17 WATTS 3000 KELVIN, CRI 90, 40K LIFE
49622 BKTLED	1200 LUMENS*, 17 WATTS 3000 KELVIN, CRI 90, 40K LIFE
49626 BKTLED	1200 LUMENS*, 17 WATTS 3000 KELVIN, CRI 90, 40K LIFE
49624 BKTLED	1200 LUMENS*, 17 WATTS 3000 KELVIN, CRI 90, 40K LIFE
49625 BKTLED	1200 LUMENS*, 17 WATTS 3000 KELVIN, CRI 90, 40K LIFE

*Initial Lumens. Visit kichler.com for recent performance and certification data.

AMBER VALLEY LED

ALUMINUM
CONSTRUCTION

	LED ITEM #	FINISH	LIGHT SOURCE	W	H	OVRLL H	EXTRA WIRE	CHAIN/STEM	EXT.	HCWO	NOTES
A	49623 BKTLED	BKT	17W	7.5	15	---	---	---	8.5	3.75	Dimmable.
B	49622 BKTLED	BKT	17W	6.5	13	---	---	---	7.5	3.75	Dimmable.
C	49626 BKTLED	BKT	17W	8.5	18.25	93	35	72	---	---	Dimmable.
D	49624 BKTLED	BKT	17W	8.75	17.25	---	---	---	10	3.75	Dimmable.
E	49625 BKTLED	BKT	17W	8.5	19.75	---	---	---	---	---	Dimmable.

Measurements shown in inches. U.S. & Canada Patent Pending.




A | **49520 AZTLED**
Indoor/Outdoor Wall



B | **49521 AZTLED**
Indoor/Outdoor Wall

CIDNEY LED

TEXTURED ARCHITECTURAL BRONZE™ FINISH
WITH SATIN ETCHED GLASS



LED OUTPUT

49520 AZTLED	1200 LUMENS*, 17 WATTS 3000 KELVIN, CRI 90, 40K LIFE
49521 AZTLED	1200 LUMENS*, 17 WATTS 3000 KELVIN, CRI 90, 40K LIFE

*Initial Lumens. Visit kichler.com for recent performance and certification data.

CIDNEY LED

ALUMINUM
CONSTRUCTION

	LED ITEM #	FINISH	LIGHT SOURCE	W	H	EXT.	HCWO	NOTES
A	49520 AZTLED	AZT	17W	5.25	13.25	6.25	3.25	Dimmable.
B	49521 AZTLED	AZT	17W	6	16	6.75	4	Dimmable.

Measurements shown in inches. U.S. & Canada Patent Pending.



C | **49519 BKTLED**
Indoor/Outdoor Wall
ADA Compliant




C | **49519 AZTLED**
Indoor/Outdoor Wall
ADA Compliant

Provides
Up and
Down Light

BRIVE™ LED

TEXTURED ARCHITECTURAL BRONZE™ OR
TEXTURED BLACK FINISH WITH
INNER SANDBLAST CLEAR GLASS



LED OUTPUT

49519 BKTLED	900 LUMENS*, 28 WATTS, 3000 KELVIN, CRI 90, 40K LIFE
49519 AZTLED	900 LUMENS*, 28 WATTS, 3000 KELVIN, CRI 90, 40K LIFE


*Initial Lumens. Visit kichler.com for recent performance and certification data.

BRIVE™ LED

ALUMINUM
CONSTRUCTION

	LED ITEM #	FINISH	LIGHT SOURCE	W	H	EXT.	NOTES
C	49519 BKTLED / 49519 AZTLED	BKT, AZT	(2) 28W	6	9	3.75	Dimmable.

Measurements shown in inches. U.S. & Canada Patent Pending.



CESYA™ LED

ARCHITECTURAL BRONZE™,
PLATINUM OR SATIN BLACK FINISH



A | **49494 PL**
Indoor/Outdoor Wall



B | **49436 PL**
Indoor/Outdoor Wall



C | **49437 PL**
Indoor/Outdoor Wall



A | **49494 SBK**
Indoor/Outdoor Wall



B | **49436 SBK**
Indoor/Outdoor Wall



C | **49437 SBK**
Indoor/Outdoor Wall



A | **49494 AZ**
Indoor/Outdoor Wall



B | **49436 AZ**
Indoor/Outdoor Wall



Side View
NOT TO SCALE



C | **49437 AZ**
Indoor/Outdoor Wall

LED OUTPUT

49494 AZ/PL/SBK	275 LUMENS*, 16 WATTS, 3000 KELVIN, CRI 80, 40K LIFE
49436 AZ/PL/SBK	550 LUMENS*, 25 WATTS, 3000 KELVIN, CRI 80, 40K LIFE
49437 AZ/PL/SBK	775 LUMENS*, 30 WATTS, 3000 KELVIN, CRI 80, 40K LIFE

*Initial Lumens. Visit kichler.com for recent performance and certification data.

CESYA™ LED

ALUMINUM
CONSTRUCTION

	LED ITEM #	FINISH	LIGHT SOURCE	W	H	EXT.	HCWO	NOTES
A	49494	AZ, PL, SBK	16W	6	12	4.75	6	
B	49436	AZ, PL, SBK	25W	6	18	4.75	9	
C	49437	AZ, PL, SBK	30W	6	24	4.75	12	

Measurements shown in inches. U.S. & Canada Patent Pending.

SEDO™ LED

ARCHITECTURAL BRONZE™,
PLATINUM OR SATIN BLACK FINISH



A | 49492 PL
Indoor/Outdoor Wall



B | 49434 PL
Indoor/Outdoor Wall



C | 49435 PL
Indoor/Outdoor Wall



A | 49492 SBK
Indoor/Outdoor Wall



B | 49434 SBK
Indoor/Outdoor Wall



C | 49435 SBK
Indoor/Outdoor Wall



A | **49492 AZ**
Indoor/Outdoor Wall
ADA Compliant



B | **49434 AZ**
Indoor/Outdoor Wall
ADA Compliant



C | **49435 AZ**
Indoor/Outdoor Wall
ADA Compliant

LED OUTPUT

49492 AZ/PL/SBK	450 LUMENS*, 16 WATTS, 3000 KELVIN, CRI 80, 40K LIFE
49434 AZ/PL/SBK	800 LUMENS*, 30 WATTS, 3000 KELVIN, CRI 80, 40K LIFE
49435 AZ/PL/SBK	800 LUMENS*, 30 WATTS, 3000 KELVIN, CRI 80, 40K LIFE

*Initial Lumens. Visit kichler.com for recent performance and certification data.

SEDO™ LED

ALUMINUM
CONSTRUCTION

	LED ITEM #	FINISH	LIGHT SOURCE	W	H	EXT.	HCWO	NOTES
A	49492	AZ, PL, SBK	16W	6	12.25	4	6.25	
B	49434	AZ, PL, SBK	30W	6	18.25	4	9.25	
C	49435	AZ, PL, SBK	30W	6	24.25	4	12.25	

Measurements shown in inches. U.S. & Canada Patent Pending.

MOUNT VERNON LED

OLDE BRONZE® FINISH OVER SOLID BRASS
WITH CLEAR SEEDED GLASS



A | 9707 OZLED
Outdoor Wall



B | 9708 OZLED
Outdoor Wall



C | 9709 OZLED
Outdoor Wall

Mount Vernon is also available in Incandescent and Energy Efficient versions. See pages 132-136.

LED OUTPUT

9707 OZLED	525 LUMENS*, 7 WATTS 3000 KELVIN, CRI 80, 20K LIFE
9708 OZLED	525 LUMENS*, 7 WATTS 3000 KELVIN, CRI 80, 20K LIFE
9709 OZLED	525 LUMENS*, 7 WATTS 3000 KELVIN, CRI 80, 20K LIFE
9809 OZLED	525 LUMENS*, 7 WATTS 3000 KELVIN, CRI 80, 20K LIFE
9909 OZLED	525 LUMENS*, 7 WATTS 3000 KELVIN, CRI 80, 20K LIFE

*Initial Lumens. Visit kichler.com for recent performance and certification data.



D | 9809 OZLED
Outdoor Pendant



Shown With
Olde Bronze™
Post 9506 OZ

E | 9909 OZLED
Post Lantern

MOUNT VERNON LED

SOLID BRASS
CONSTRUCTION

	LED ITEM #	FINISH	LIGHT SOURCE	W	H	OVRL. H	EXTRA WIRE	CHAIN/STEM	EXT.	HCWO	NOTES
A	9707 OZLED	OZ	7W	5.5	12.5	---	---	---	6.25	5.5	Dimmable.
B	9708 OZLED	OZ	7W	7.5	16.75	---	---	---	8.25	6.75	Dimmable.
C	9709 OZLED	OZ	7W	9.5	19.5	---	---	---	10.25	7.25	Dimmable.
D	9809 OZLED	OZ	7W	9.5	18.5	93	34	72	---	---	Additional chain 4927 OZ. Dimmable.
E	9909 OZLED	OZ	7W	9.5	20.75	---	---	---	---	---	Dimmable.

Measurements shown in inches.

Hatteras Bay™ is also available in Incandescent. See page 74-76.

FC

These devices comply with part 15 of the FCC Regulations.

HATTERAS BAY™ LED

OLDE BRONZE® FINISH WITH CLEAR FRESNEL GLASS



A | 49067 OZLED
Indoor/Outdoor Wall



B | 49065 OZLED
Indoor/Outdoor Wall

LED OUTPUT

49065 OZLED	800 LUMENS*, 10 WATTS 3000 KELVIN, CRI 80, 20K LIFE
49067 OZLED	800 LUMENS*, 10 WATTS 3000 KELVIN, CRI 80, 20K LIFE

*Initial Lumens. Visit kichler.com for recent performance and certification data.

HATTERAS BAY™ LED

ALUMINUM & SOLID BRASS CONSTRUCTION

	LED ITEM #	FINISH	LIGHT SOURCE	W	H	EXT.	HCWO	NOTES
A	49067 OZLED	OZ	10W	10.5	10.25	11.75	4	Dimmable.
B	49065 OZLED	OZ	10W	8.75	9.5	10	3.5	Dimmable.

Measurements shown in inches. U.S. & Canada Patent Pending.



C | 49253 AZTLED
Indoor/Outdoor Wall



D | 49252 AZTLED
Indoor/Outdoor Wall
ADA Compliant

SHELBY LED

TEXTURED ARCHITECTURAL BRONZE™ FINISH WITH INNER SANDBLASTED CLEAR GLASS

FC

These devices comply with part 15 of the FCC Regulations.

LED OUTPUT

49252 AZTLED	450 LUMENS*, 14 WATTS 3000 KELVIN, CRI 90, 40K LIFE
49253 AZTLED	1100 LUMENS*, 28 WATTS 3000 KELVIN, CRI 90, 40K LIFE

*Initial Lumens. Visit kichler.com for recent performance and certification data.

SHELBY LED

ALUMINUM CONSTRUCTION

	LED ITEM #	FINISH	LIGHT SOURCE	W	H	L	EXT.	HCWO	NOTES
C	49253 AZTLED	AZT	(2) 28W	7.5	11	5.75	5.75	5.5	Dimmable.
D	49252 AZTLED	AZT	14W	5.25	6	4	4	3	Dimmable.

Measurements shown in inches. U.S. & Canada Patent Pending.

MAYA PALM™ LED

AGED BRONZE FINISH



A | 49248 AGZLED
Outdoor Wall

B | 49249 AGZLED
Outdoor Wall



These devices
comply with part 15
of the FCC Regulations.

LED OUTPUT

49248 AGZLED	225 LUMENS*, 8 WATTS 3000 KELVIN, CRI 80, 40K LIFE
49249 AGZLED	350 LUMENS*, 11 WATTS 3000 KELVIN, CRI 83, 40K LIFE

*Initial Lumens. Visit kichler.com for recent performance and certification data.

CAST ALUMINUM
CONSTRUCTION

MAYA PALM™ LED

	LED ITEM #	FINISH	LIGHT SOURCE	W	H	EXT.	HCWO	NOTES
A	49248 AGZLED	AGZ	8W	7.75	10.75	5.75	3.25	
B	49249 AGZLED	AGZ	11W	9.5	13.25	6.75	4	

Measurements shown in inches. U.S. & Canada Patent Pending.

FRANCEASI™ LED

OLDE BRONZE® FINISH



A | **49226 OZLED**
Indoor/Outdoor Wall



B | **49227 OZLED**
Indoor/Outdoor Wall



C | **49228 OZLED**
Indoor/Outdoor Wall



D | **49229 OZLED**
Indoor/Outdoor Wall

MATCHING COLLECTION

See entire Incandescent
Franceasi™ Collection
on pages 60-61.



These devices
comply with part 15
of the FCC Regulations.

LED OUTPUT

49226 OZLED	276 LUMENS*, 8 WATTS 3000 KELVIN, CRI 80, 40K LIFE
49227 OZLED	350 LUMENS*, 11 WATTS 3000 KELVIN, CRI 83, 40K LIFE
49228 OZLED	325 LUMENS*, 11 WATTS 3000 KELVIN, CRI 80, 40K LIFE
49229 OZLED	400 LUMENS*, 11 WATTS 3000 KELVIN, CRI 80, 40K LIFE

*Initial Lumens. Visit kichler.com for recent performance and certification data.

FRANCEASI™ LED

CAST ALUMINUM
CONSTRUCTION

	LED ITEM #	FINISH	LIGHT SOURCE	W	H	EXT.	HCWO	NOTES
A	49226 OZLED	OZ	8W	5.5	14.5	7.25	4.5	
B	49227 OZLED	OZ	11W	7	18	9	5.75	
C	49228 OZLED	OZ	11W	8.5	22	10.5	7.5	
D	49229 OZLED	OZ	11W	10	25	12.25	8.75	

Measurements shown in inches. U.S. & Canada Patent Pending.

WALDEN LED

ARCHITECTURAL BRONZE™ OR
TEXTURED BLACK FINISH




A | **49550 AZLED**
Indoor/Outdoor Wall
ADA Compliant



A | **49550 BKTLED**
Indoor/Outdoor Wall
ADA Compliant



B | **49551 AZLED**
Indoor/Outdoor Wall
ADA Compliant



B | **49551 BKTLED**
Indoor/Outdoor Wall
ADA Compliant

Clear Glass with
Inside Etch

Provides Up and
Down Lighting



These devices
comply with part 15
of the FCC Regulations.

LED OUTPUT

49550 AZLED/ BKTLED	720 LUMENS*, 10 WATTS, 3000 KELVIN, CRI 90, 35K LIFE
49551 AZLED/ BKTLED	1440 LUMENS*, 20 WATTS, 3000 KELVIN, CRI 90, 40K LIFE

*Initial Lumens. Visit kichler.com for recent performance and certification data.

ALUMINUM
CONSTRUCTION

WALDEN LED

	ITEM #	FINISH	LIGHT SOURCE	W	H	EXT.	HCWO	NOTES
A	49550 AZLED / 49550 BKTLED	AZT, BKT	10W	5	7.5	3.75	3.75	Dimmable
B	49551 AZLED / 49551 BKTLED	AZT, BKT	20W	5	12	3.75	6	Dimmable.

Measurements shown in inches. U.S. & Canada Patent Pending.



These devices comply with part 15 of the FCC Regulations.

LED WALL

TEXTURED ARCHITECTURAL BRONZE™
OR TEXTURED BLACK FINISH



A | **11250 AZT30**
Indoor/Outdoor Wall



A | **11250 BKT30**
Indoor/Outdoor Wall



C | **11077 AZT**
Indoor/Outdoor Wall



B | **11251 AZT30**
Indoor/Outdoor Wall



B | **11251 BKT30**
Indoor/Outdoor Wall



C | **11077 BKT**
Indoor/Outdoor Wall

LED OUTPUT

11077 AZT/BKT	400 LUMENS*, 15 WATTS, 3000 KELVIN, CRI 90, 40K LIFE
11250 AZT30/ 11250 BKT30	350 LUMENS*, 10 WATTS, 3000 KELVIN, CRI 80, 40K LIFE
11251 AZT30/ 11251 BKT30	550 LUMENS*, 15 WATTS, 3000 KELVIN, CRI 80, 40K LIFE

*Initial Lumens. Visit kichler.com for recent performance and certification data.

LED WALL

CAST ALUMINUM
CONSTRUCTION

	LED ITEM #	FINISH	LIGHT SOURCE	W	H	EXT.	HCWO	NOTES
A	11250 AZT30 / 11250 BKT30	AZT, BKT	(1) 10W	5	7	6.5	3.25	
B	11251 AZT30 / 11251 BKT30	AZT, BKT	(2) 15W	5	12	6.5	6.25	
C	11077 AZT30 / 11077 BKT30	AZT, BKT	(1) 15W	5	5.5	6	2.75	

Measurements shown in inches.

OUTDOOR WALL

ASSORTED FINISHES



A | 9234 AZ
Outdoor Wall



Brushed
Alluminum

A | 9234 BA
Outdoor Wall



A | 9234 WH
Outdoor Wall



B | 9236 AZ
Outdoor Wall



C | 9834 WH
Outdoor Ceiling

OUTDOOR WALL

ITEM #	FINISH	INCAND. BULB	W	H	EXT.	HCWO	NOTES
A 9234	AZ, BA, WH	(1) 65W (M) BR-30	4.75	7	7	3.5	Ⓜ Ⓞ Ⓜ Ⓞ (13-15W CFL)
B 9236	AZ	(1) 120W (M) BR-40	6	7.75	8.5	4	Ⓜ Ⓞ Ⓜ Ⓞ (13-15W CFL)
C 9834	WH	(1) 65W (M) BR-30 ❖	4.5	8.5	---	---	Ⓜ Ⓞ Ⓜ Ⓞ (23-30W CFL)
D 9244	AZ, BA, WH	(2) 65W (M) BR-30	4.75	12	7	6	Ⓜ Ⓞ Ⓜ Ⓞ (13-15W CFL)
E 9246	AZ, BA, WH	(2) 120W (M) BR-40	6	15	8.5	7.5	Ⓜ Ⓞ Ⓜ Ⓞ (23-30W CFL)

Measurements shown in inches.



D | 9244 AZ
Outdoor Wall



Brushed
Alluminum

D | 9244 BA
Outdoor Wall



D | 9244 WH
Outdoor Wall



E | 9246 AZ
Outdoor Wall



E | 9246 BA
Outdoor Wall



E | 9246 WH
Outdoor Wall

LENS ACCESSORIES

9534 BK

GLASS LENS USE WITH
9234, 9244

9536 BK

GLASS LENS USE WITH
9236, 9246

Convert open top units to outdoor applications. Heat-resistant glass lens with black frame.



9534 BK



9536 BK

BRIGHTNESS CONTROL ACCESSORIES

9544 BK

GROOVED BAFFLE
USE WITH 9234, 9244

9546 BK

GROOVED BAFFLE
USE WITH 9236, 9246

Grooved black plastic baffles achieve low, even surface brightness.



9544 BK



9546 BK

CELINO™

BRUSHED ALUMINUM OR BLACK WITH
ETCHED OPAL GLASS



A | 9109 BA
Indoor/Outdoor Wall



A | 9109 BK
Indoor/Outdoor Wall

CELINO™

ALUMINUM
CONSTRUCTION

ITEM #	FINISH	INCAND. BULB	W	H	EXT.	HCWO	NOTES
A 9109	BA, BK	(1) 100W (M)	5	13.25	5	10.25	W EOD (23-30W CFL)

Measurements shown in inches.

NEWPORT™

ARCHITECTURAL BRONZE™ OR BRUSHED
NICKEL FINISH WITH WHITE ACRYLIC
DIFFUSER & HOUSING



B | 6040 AZ
10640 AZ
Indoor/Outdoor Wall
ADA Compliant



B | 6040 NI
10640 NI
Indoor/Outdoor Wall
ADA Compliant

White Acrylic
Diffuser and
Housing



C | 6048 AZ
Indoor/Outdoor Wall
ADA Compliant



C | 6048 NI
Indoor/Outdoor Wall
ADA Compliant

NEWPORT™

ITEM #	FLUOR. ITEM #	FINISH	INCAND. BULB	FLUOR. BULB	W	H	EXT.	HCWO	NOTES
B 6040	10640	AZ, NI	(1) 30W CFL (M) or (1) 60W Incand. (M)	(1) 18W (GU24)	9.25	10.25	3.75	5	AZ: Powder coated aluminum/polycarbonate construction, NI: 304 stainless steel/polycarbonate construction.
C 6048	---	AZ, NI	(2) 30W CFL (M) or (2) 40W Incand. (M)	---	9.25	15.25	3.75	7.75	AZ: Powder coated aluminum/polycarbonate construction, NI: 304 stainless steel/polycarbonate construction.

Measurements shown in inches.

ZOLDER™

ARCHITECTURAL BRONZE™ WITH
SATIN ETCHED CASED OPAL GLASS



A | 49149 AZ
Indoor/Outdoor Wall



Aluminum Construction

B | 49151 AZ
Indoor/Outdoor Wall

ZOLDER™

ALUMINUM
CONSTRUCTION

	ITEM #	FINISH	INCAND. BULB	W	H	EXT.	HCWO	NOTES
A	49149	AZ	(1) 60W (K)	4.5	17	4.5	10.75	Krypton light source.
B	49151	AZ	(2) 60W (K)	4.5	26.5	4.25	13.25	Krypton light source.

Measurements shown in inches. U.S. & Canada Patent Pending.



OUTDOOR LIVING

WHY STAY INDOORS WHEN YOU CAN
TAKE THE PARTY OUTSIDE?

Gone are the days of the simple patio; today's outdoor spaces are extensions of our homes with kitchens, dining rooms, living rooms and more designed to breathe fresh life into our days and nights.

The Kichler Outdoor Living collection draws inspiration from some of our favorite interior fixtures, yet is designed to weather life outside. Chandeliers, pendants, sconces, ceiling fans – they all feature decorative touches and corrosion-resistant finishes. Take your pick, and watch how they transform a space with style and light.





INDOOR/OUTDOOR CHANDELIERS

ASSORTED FINISHES & GLASS



A | 49671 AZ
Indoor/Outdoor Chandelier
Hendrik™



B | 49696 BKT
Indoor/Outdoor Chandelier
Harvest Ridge™



C | 49590 OZ
Indoor/Outdoor Chandelier
Larkin™



D | 49498 AZ
Indoor/Outdoor Chandelier
Lyndon™



E | 49667 WZC
Indoor/Outdoor Chandelier
Ashland Bay

INDOOR/OUTDOOR CHANDELIERS

ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/STEM	NOTES
A	49671 AZ	(5) 100W (M)	25	21.5	60	75	36	Ⓛ E26 (23-30W CFL) Additional chain 4927 AZ, additional stem (12") 2999 AZ. Sloped ceiling kit included. Satin Etched Cased Opal Glass.
B	49696 BKT	(3) 100W (M)	25	7.25	46	110	36	Ⓛ Additional stem (12") 2999 BKT.
C	49590 OZ	(4) 100W (M)	18	36.75	111	6	72	Ⓛ E26 (23-30W CFL) Additional chain 4927 OZ. Satin Etched Cased Opal Glass.
D	49498 AZ	(5) 75W (M)	24	9.75	48	110	36	Ⓛ Additional chain 4927 AZ, additional stem (12") 2999 AZ. Sloped ceiling kit included. Clear Seeded Glass.
E	49667 WZC	(5) 60W (M)	26	20	58	110	36	Ⓛ E26 (13-15W CFL) Additional chain 4927 WZC, additional stem (12") 2999 WZC. Sloped ceiling kit included. Clear Seeded Ribbed Glass.

Measurements shown in inches. U.S. & Canada Patent Pending.



F | 49588 OZ
Indoor/Outdoor Chandelier
Westington™



G | 49603 LD
Indoor/Outdoor Chandelier
Halleron™



H | 49091 CV
Indoor/Outdoor Chandelier
Alameda™



J | 49638 OZ
Indoor/Outdoor Chandelier
Caterham™

INDOOR/OUTDOOR CHANDELIERS

CAST ALUMINUM
CONSTRUCTION

ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	L	EXTRA WIRE	CHAIN/STEM	NOTES	
F	49588	OZ	(3) 100W (M)	8	7.25	46	32	60	36	Ⓧ Additional chain 4927 OZ, additional stem 2999 (12") OZ. Sloped ceiling kit included.
G	49603	LD	(3) 60W (C)	12	18.5	93	---	23	72	Ⓧ Additional chain 4927 LD. Clear Seeded Glass.
H	49091	CV	(4) 100W (M)	25	17	55	---	59	36	Ⓧ Additional chain 4927 CV, additional stem 2999 (12") CV. Sloped ceiling kit included. Honey Opalescent Glass.
J	49638	OZ	(4) 100W (M)	21	12.75	51	---	67	36	Ⓧ EOD (23-30W CFL) Additional chain 4927 OZ, additional stem 2999 (12") OZ. Sloped ceiling kit included. Satin Etched Cased Opal Glass.

Measurements shown in inches. U.S. & Canada Patent Pending, E & F.

OUTDOOR FAN OVERVIEW



SKU	310140
Blades	Olde Bronze®
Finishes	OZ
Glass	Clear Seeded



SKU	370060
Blades	Olde Bronze® Aluminum
Finishes	OZ
Glass	N/A



SKU	310115
Blades	Distressed Black
Finishes	ANS, CMO, DBK
Glass	N/A



SKU	310110
Blades	Mediterranean Walnut™
Finishes	MDW
Glass	Etched Opal



SKU	310136
Blades	Olde Bronze®
Finishes	OZ
Glass	Etched Cased Opal



SKU	310131
Blades	Walnut
Finishes	OZ
Glass	White Cased Opal



TZP

SKU	310102
Blades	Cherry All Weather ABS
Finishes	TZP
Glass	Fresnel Lens



DBK

SKU	310103
Blades	Walnut Shadowed
Finishes	DBK
Glass	N/A



WSP

SKU	310215
Blades	Champagne
Finishes	AZT, WSP
Glass	Etched Cased Opal



TZP

SKU	310192
Blades	Cherry All Weather ABS
Finishes	TZP
Glass	N/A



TZP

SKU	310117
Blades	Tannery Bronze® Powder Coat
Finishes	TZP
Glass	Fresnel Lens



Ceiling Fan Catalog K416
 To view our extensive ceiling fan offering, visit kichler.com or request our ceiling fan catalog K416.



Lyndon™ Pendant 49447 AZ | Page 51

LYNDON™

ARCHITECTURAL BRONZE™ FINISH
WITH CLEAR SEEDED GLASS



A | 49498 AZ
Indoor/Outdoor Chandelier

LYNDON™

ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/STEM	NOTES
A 49498	AZ	(5) 75W (M)	24	9.75	48	110	36	ⓓ Additional chain 4927 AZ, additional stem 2999 (12") AZ. Sloped ceiling kit included.

Measurements shown in inches. U.S. & Canada Patent Pending.

LYNDON™

ARCHITECTURAL BRONZE™ FINISH
WITH CLEAR SEEDED GLASS



Shown with Vintage Filament Bulb, 40W Candelabra Base 5971 CLR

Can Only Be Mounted with Glass Facing Down for Outdoor Use

A | 49444 AZ
Indoor/Outdoor Wall

B | 49445 AZ
Indoor/Outdoor Wall

C | 49496 AZ
Indoor/Outdoor Wall

LYNDON™

CAST ALUMINUM
CONSTRUCTION

ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/STEM	EXT.	HCWO	NOTES	
A	49444	AZ	(1) 75W (M)	5	11.25	---	---	---	7.5	3.75	W 30D (18-25W CFL) Indoor/Outdoor.
B	49445	AZ	(1) 100W (M)	6	15	---	---	---	8	5	W 30D (23-30W CFL) Indoor/Outdoor.
C	49496	AZ	(2) 60W (C)	8	18.25	---	---	---	9.5	5	W Indoor/Outdoor.
D	49446	AZ	(1) 75W (M)	5	9.5	48	72	36	---	---	D 30D (18-25W CFL) Add. chain 4927 AZ, add. stem 2999 (12") AZ. Indoor/Outdoor. Sloped ceiling kit included.
E	49447	AZ	(1) 100W (M)	6	11.75	50	71	36	---	---	D 30D (23-30W CFL) Add. chain 4927 AZ, add. stem 2999 (12") AZ. Indoor/Outdoor. Sloped ceiling kit included.
F	49497	AZ	(1) 100W (M)	10	20	---	---	---	---	---	W

Measurements shown in inches. U.S. & Canada Patent Pending.



D | 49446 AZ
Indoor/Outdoor Pendant



E | 49447 AZ
Indoor/Outdoor Pendant



Shown with
Architectural Bronze™
Post, 9506 AZ

F | 49497 AZ
Post Lantern



**VINTAGE
FILAMENT
BULB**

SOLD SEPARATELY
40W Candelabra Base
5971 CLR



**VINTAGE
FILAMENT
BULB**

SOLD SEPARATELY
60W Medium Base
4071 CLR

LYNDON™

BRUSHED ALUMINUM FINISH WITH
CLEAR SEEDED GLASS



LYNDON™

CAST ALUMINUM
CONSTRUCTION

ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/STEM	EXT.	HCWO	NOTES	
A	49444	BA	(1) 75W (M)	5	11.25	---	---	---	7.5	3.75	W 0D (18-25W CFL) Indoor/Outdoor.
B	49445	BA	(1) 100W (M)	6	15	---	---	---	8	5	W 0D (23-30W CFL) Indoor/Outdoor.
C	49496	BA	(2) 60W (C)	8	18.25	---	---	---	9.5	5	W Indoor/Outdoor.
D	49446	BA	(1) 75W (M)	5	9.5	48	72	36	---	---	D 0D (18-25W CFL) Add. chain 4927 BA, add. stem 2999 (12") BA. Sloped ceiling kit included.
E	49447	BA	(1) 100W (M)	6	11.75	50	71	36	---	---	D 0D (23-30W CFL) Add. chain 4927 BA, add. stem 2999 (12") BA. Sloped ceiling kit included.
F	49497	BA	(1) 100W (M)	10	20	---	---	---	---	---	W

Measurements shown in inches. U.S. & Canada Patent Pending.



D | 49446 BA
Indoor/Outdoor Pendant



E | 49447 BA
Indoor/Outdoor Pendant



F | 49497 BA
Post Lantern



**VINTAGE
FILAMENT
BULB**

SOLD SEPARATELY
40W Candelabra Base
5971 CLR



**VINTAGE
FILAMENT
BULB**

SOLD SEPARATELY
60W Medium Base
4071 CLR

SOUTH HOPE™

RUBBED BRONZE™ FINISH WITH
SATIN ETCHED CASED OPAL GLASS



A | 49474 RZ
Outdoor Wall



B | 49475 RZ
49475 RZFL
Outdoor Wall



C | 49476 RZ
49476 RZFL
Outdoor Wall

CAST ALUMINUM
CONSTRUCTION

SOUTH HOPE™

ITEM #	FLOUR ITEM #	FINISH	INCAND. BULB	FLOUR. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/STEM	EXT.	HCWO	NOTES	
A	49474	---	RZ	(1) 60W (C)	---	5.5	11.75	---	---	---	6.25	7.25	W B-type lamp recommended.
B	49475	49475 RZFL	RZ	(1) 60W (M)	(1) 13W (GU24)	7	17.75	---	---	---	7.75	9.5	W OD (13-15W CFL)
C	49476	49476 RZFL	RZ	(1) 100W (M)	(1) 18W (GU24)	9	19.75	---	---	---	9.5	11.74	W OD (23-30W CFL) Variable height mounting hardware included, Junction box 10"-13.25".
D	49493	---	RZ	(1) 100W (M)	---	9	19	93	70	72	---	---	D OD (23-30W CFL)
E	49499	---	RZ	(2) 60W (M)	---	9	28	---	---	---	9.75	16	W OD (13-15W CFL)
F	49478	---	RZ	(1) 100W (M)	---	9	21.5	---	---	---	---	---	W OD (23-30W CFL) Convertible from post to column mount.

Measurements shown in inches. U.S. & Canada Patent Pending.



D | 49493 RZ
Outdoor Pendant



E | 49499 RZ
Outdoor Wall



Post Lantern

Shown with
Architectural Bronze™
Post, 9505 AZ

CONVERTIBLE

Create two distinct lighting
options with one fixture:
Post Lantern or Column Mount
Lantern Installation Options.
Hardware included.

F | 49478 RZ



Column Mount

CAMDEN™

ANVIL IRON FINISH WITH
OPAL ETCHED GLASS



A | 49119 AVI
49119 AVIFL
Outdoor Wall



B | 49120 AVI
49120 AVIFL
Outdoor Wall



C | 49121 AVI
49121 AVIFL
Outdoor Wall

CAMDEN™

CAST ALUMINUM
CONSTRUCTION

ITEM #	FLOUR. ITEM #	FINISH	INCAND. BULB	FLOUR. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/STEM	EXT.	HCWO	NOTES	
A	49119	49119 AVIFL	AVI	(1) 100W (M)	(1) 13W (GU24)	5	11	---	---	---	5.75	5.5	OD (23-30W CFL)
B	49120	49120 AVIFL	AVI	(2) 100W (M)	(2) 18W (GU24)	6.25	19.5	---	---	---	7.25	9.75	OD (23-30W CFL)
C	49121	49121 AVIFL	AVI	(2) 75W (M)	(2) 18W (GU24)	7.25	22.5	---	---	---	8.25	11.25	OD (18-25W CFL)
D	49122	49122 AVIFL	AVI	(3) 100W (M)	(3) 18W (GU24)	9	26	---	---	---	11.25	5.75-21.5	OD (23-30W CFL)
E	49124	---	AVI	(1) 150W (M)	---	9.5	18.75	93	24	72	---	---	OD (30-52W CFL)
F	49125	---	AVI	(1) 75W (M) ✓	---	9.75	5.5	---	---	---	---	---	OD (18-25W CFL)
G	49123	---	AVI	(1) 150W (M)	---	9.5	17	---	---	---	---	---	OD (30-52W CFL)

Measurements shown in inches.



D | 49122 AVI
49122 AVIFL
Outdoor Wall



E | 49124 AVI
Outdoor Pendant



F | 49125 AVI
Outdoor Ceiling



Shown with
Black Post
9595 BK

G | 49123 AVI
Post Lantern

TREMILLO™

BLACK FINISH WITH
SATIN ETCHED CASÉD OPAL GLASS



A | 49200 BK
49200 BKFL
Outdoor Wall

























B | 49201 BK
49201 BKFL
Outdoor Wall



C | 49202 BK
49202 BKFL
Outdoor Wall

CAST ALUMINUM
CONSTRUCTION

TREMILLO™

ITEM #	FLUOR. ITEM #	FINISH	INCAND. BULB	FLUOR. BULB	W	H	OVRL. H	L	EXTRA WIRE	CHAIN/STEM	EXT.	HCWO	NOTES	
A	49200	49200 BKFL	BK	(1) 100W (M)	(1) 13W (GU24)  	5.75	11.75	---	---	---	---	6.75	5	 30D (18-25W CFL)
B	49201	49201 BKFL	BK	(1) 100W (M)	(1) 13W (GU24)  	7	14.25	---	---	---	---	8	6	 30D (23-30W CFL)
C	49202	49202 BKFL	BK	(1) 150W (M)	(1) 18W (GU24)  	8.5	17.25	---	---	---	---	9.75	7.25	 30D (30-52W CFL)
D	49203	49203 BKFL	BK	(1) 150W (M)	(1) 18W (GU24)  	10	20.25	---	---	---	---	11.25	8.5	 30D (30-52W CFL)
E	49206	49206 BKFL	BK	(2) 60W (M) 	(2) 18W (GU24)  	11.5	6.5	---	---	---	---	---	---	 30D (9-13W CFL)
F	49205	49205 BKFL	BK	(1) 100W (M)	(1) 18W (GU24)  	6.5	17	91	7	25	72	---	---	 30D (23-30W CFL) Additional chain 4927 BK.
G	49207	49207 BKFL	BK	(1) 150W (M)	(1) 18W (GU24)  	8.25	20	---	8.5	---	---	---	---	 30D (30-52W CFL)

Measurements shown in inches. U.S. & Canada Patent Pending.



D | 49203 BK
49203 BKFL
Outdoor Wall



E | 49206 BK
49206 BKFL
Outdoor Ceiling



F | 49205 BK
49205 BKFL
Outdoor Pendant



Shown with
Black Post 9506BK

G | 49207 BK
49207 BKFL
Post Lantern

FRANCEASI™

OLDE BRONZE® FINISH WITH
LIGHT UMBER ETCHED SEEDED GLASS



A | 49226 OZ
Outdoor Wall



B | 49227 OZ
Outdoor Wall



C | 49228 OZ
Outdoor Wall

Franceasi™
is also available
in LED.
See page 35.



D | 49229 OZ
Outdoor Wall



E | 49232 OZ
Outdoor Ceiling

CAST ALUMINUM
CONSTRUCTION

FRANCEASI™

	ITEM #	FINISH	INCAND. BULB	W	H	EXT.	HCWO	NOTES
A	49226	OZ	(1) 100W (M)	5.5	14.5	7.25	4.5	W EOD (18-25W CFL)
B	49227	OZ	(1) 100W (M)	7	18	9	5.75	W EOD (23-30W CFL)
C	49228	OZ	(1) 100W (M)	8.5	22	10.5	7.5	W EOD (23-30W CFL)
D	49229	OZ	(1) 150W (M)	10	25	12.25	8.75	W EOD (30-52W CFL)
E	49232	OZ	(2) 60W (M) ❖	11	6.5	---	---	D EOD (13-15W CFL)

Measurements shown in inches. U.S. & Canada Patent Pending.

PACIFIC EDGE™

ARCHITECTURAL BRONZE™ FINISH WITH
SATIN ETCHED CASED OPAL GLASS



A | 49344 AZ
49344 AZFL
Outdoor Wall












C | 49346 AZ
49346 AZFL
Outdoor Wall



B | 49345 AZ
49345 AZFL
Outdoor Wall

PACIFIC EDGE™

	ITEM #	FLOUR. ITEM #	FINISH	INCAND. BULB	FLOUR. BULB	W	H	EXT.	HCWO	NOTES
A	49344	49344 AZFL	AZ	(1) 75W (M)	(1) 18W (GU24)  	6	10.75	6.5	7	 30D (18-25W CFL)
B	49345	49345 AZFL	AZ	(1) 100W (M)	(1) 18W (GU24)  	8	13.25	8.75	9.25	 30D (23-30W CFL)
C	49346	49346 AZFL	AZ	(1) 150W (M)	(1) 26W (GU24)  	9.5	16	10.25	11.5	 30D (30-52W CFL)

Measurements shown in inches. U.S. & Canada Patent Pending.



D | 49348 AZ
Outdoor Pendant



E | 9557 AZ
Outdoor Ceiling



F | 49349 AZ
Post Lantern

Shown with
Architectural
Bronze™ Post
9506 AZ

PACIFIC EDGE™

CAST ALUMINUM
CONSTRUCTION

ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/STEM	NOTES
D	AZ	(1) 100W (M)	8	13.5	52	64	36	D E0D (23-30W CFL) Additional chain 2996 AZ, additional stem 2999 (12") AZ. Sloped ceiling kit included.
E	AZ	(1) 100W (M)	10.5	6.25	---	---	---	D E0D (23-30W CFL)
F	AZ	(1) 150W (M)	9.5	19	---	---	---	W E0D (30-52W CFL)

Measurements shown in inches. U.S. & Canada Patent Pending.

PACIFIC EDGE™

POLISHED STAINLESS STEEL MARINE GRADE 316
WITH SATIN ETCHED CASED OPAL GLASS



A | 49344 PSS316
Outdoor Wall



B | 49345 PSS316
Outdoor Wall



C | 49346 PSS316
Outdoor Wall



Shown with
Brushed Aluminum
Post 9506 BK

D | 49349 PSS316
Post Lantern

LifeBrite™
BY KICHLER®

Kichler's LifeBrite™ Finish has a lifetime finish guarantee to withstand the harshest elements, salt air and extreme weather conditions.

**MARINE GRADE 316
STAINLESS STEEL
CONSTRUCTION**

PACIFIC EDGE™

ITEM #	FINISH	INCAND. BULB	W	H	EXT.	HCWO	NOTES	
A	49344	PSS316	(1) 75W (M)	6	10.75	6.5	7	W EOD (18-25W CFL)
B	49345	PSS316	(1) 100W (M)	8	13.25	8.75	9.25	W EOD (23-30W CFL)
C	49346	PSS316	(1) 150W (M)	9.5	16	10.25	11.5	W EOD (30-52W CFL)
D	49349	PSS316	(1) 150W (M)	9.5	19	---	---	W EOD (30-52W CFL)

Measurements shown in inches. U.S. & Canada Patent Pending.

McADAMS™

RUBBED BRONZE™ FINISH WITH
LIGHT UMBER ETCHED SEEDED GLASS



A | 49270 RZ
Outdoor Wall



B | 49271 RZ
Outdoor Wall



C | 49272 RZ
Outdoor Wall



D | 49273 RZ
Outdoor Wall



E | 49274 RZ
Post Lantern

McADAMS™

CAST ALUMINUM
CONSTRUCTION

	ITEM #	FINISH	INCAND. BULB	W	H	L	EXT.	HCWO	NOTES
A	49270	RZ	(1) 100W (M)	5.5	9.5	6.75	6.75	5.25	W EOD (18-25W CFL)
B	49271	RZ	(1) 100W (M)	8	14	9.5	9.5	6.5	W EOD (23-30W CFL)
C	49272	RZ	(1) 150W (M)	10	17.5	---	11.5	8	W EOD (30-52W CFL)
D	49273	RZ	(1) 150W (M)	12	21	---	14.25	9	W EOD (30-52W CFL)
E	49274	RZ	(1) 150W (M)	10	22.25	---	---	---	W EOD (30-52W CFL)

Measurements shown in inches. U.S. & Canada Patent Pending.

LANTANA™

ARCHITECTURAL BRONZE™ FINISH
WITH LIGHT UMBER GLASS



A | 9166 AZ
11067 AZFL
Outdoor Wall



B | 9167 AZ
11068 AZFL
Outdoor Wall



C | 9168 AZ
11069 AZFL
Outdoor Wall



D | 9967 AZ
Post Lantern

Shown with
Architectural Bronze™
Post 9506 AZ

CAST ALUMINUM
CONSTRUCTION

LANTANA™

ITEM #	FLOUR. ITEM #	FINISH	INCAND. BULB	FLOUR. BULB	W	H	EXT.	HCWO	NOTES
A	9166 11067 AZFL	AZ	(1) 75W (M)	(1) 13W (GU24)	7	10	5.9	3.25	0D (18-25W CFL)
B	9167 11068 AZFL	AZ	(1) 100W (M)	(1) 13W (GU24)	9	13	7.5	4	0D (23-30W CFL)
C	9168 11069 AZFL	AZ	(1) 150W (M)	(1) 18W (GU24)	10.5	15.25	8.75	4	0D (23-30W CFL)
D	9967 ---	AZ	(1) 150W (M)	---	10.5	19.5	---	---	0D (23-30W CFL)

Measurements shown in inches. U.S. & Canada Patent Pending.

ATWOOD

BROWN STONE FINISH WITH
LIGHT UMBER MIST GLASS



A | 49073 BST
49073 BSTFL
Outdoor Wall



B | 49072 BST
49072 BSTFL
Outdoor Wall



C | 49071 BST
49071 BSTFL
Outdoor Wall



D | 49075 BST
49075 BSTFL
Outdoor Pendant



Shown with
Brown Stone
Post 9595 BST

E | 49074 BST
49074 BSTFL
Post Lantern

CAST ALUMINUM
CONSTRUCTION

ATWOOD

ITEM #	FLUOR. ITEM #	FINISH	INCAND. BULB	FLUOR. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/STEM	EXT.	HCWO	NOTES
A	49073	49073 BSTFL	BST	(1) 150W (M) (1) 18W (GU24)	10	17.75	---	---	---	11	3.25	30D (30-52W CFL)
B	49072	49072 BSTFL	BST	(1) 100W (M) (1) 18W (GU24)	8	14.25	---	---	---	9	3	30D (23-30W CFL)
C	49071	49071 BSTFL	BST	(1) 100W (M) (1) 13W (GU24)	6	11	---	---	---	7	2.5	30D (23-30W CFL)
D	49075	49075 BSTFL	BST	(1) 150W (M) (1) 18W (GU24)	10	17.75	92	23	72	---	---	30D (23-30W CFL) Add. chain 4927 BST
E	49074	49074 BSTFL	BST	(1) 150W (M) (1) 18W (GU24)	10	22.25	---	---	---	---	---	30D (30-52W CFL)

Measurements shown in inches.

BOWEN™

ARCHITECTURAL BRONZE™ FINISH WITH
SATIN ETCHED CASED OPAL GLASS



A | 49336 AZ
Outdoor Wall



B | 49337 AZ
Outdoor Wall



C | 49338 AZ
Outdoor Wall



D | 49339 AZ
Outdoor Wall

BOWEN™

ITEM #	FINISH	INCAND. BULB	W	H	EXT.	HCWO	NOTES
A	AZ	(1) 75W (M)	5.5	9.5	6.5	4	W 30D (18-25W CFL)
B	AZ	(1) 100W (M)	7.25	13	8.5	5.75	W 30D (23-30W CFL)
C	AZ	(1) 150W (M)	9	15.75	10.25	7	W 30D (30-52W CFL)
D	AZ	(2) 100W (M)	7.25	18	8.5	5.75	W 30D (23-30W CFL)

Measurements shown in inches. U.S. & Canada Patent Pending.



E | 49341 AZ
Outdoor Pendant



F | 49343 AZ
Outdoor Ceiling



Shown with
Architectural Bronze™
Post 9506 AZ

G | 49342 AZ
Post Lantern

BOWEN™

	ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/STEM	NOTES
E	49341	AZ	(2) 100W (M)	7.25	20.25	95	27	72	Ⓚ Ⓜ Ⓜ (23-30W CFL) Additional chain 4927 AZ.
F	49343	AZ	(2) 75W (M) ✓	11	6.5	---	---	---	Ⓚ Ⓜ Ⓜ (18-25W CFL)
G	49342	AZ	(1) 150W (M)	9	18.5	---	---	---	Ⓚ Ⓜ Ⓜ (30-52W CFL)

Measurements shown in inches. U.S. & Canada Patent Pending.

ASHLAND BAY

WEATHERED ZINC FINISH WITH
CLEAR SEEDED RIBBED GLASS



A | 49569 WZC
Indoor/Outdoor Wall



B | 49570 WZC
Indoor/Outdoor Wall



C | 49571 WZC
Indoor/Outdoor Wall



D | 49668 WZC
Indoor/Outdoor Wall

ALUMINUM
CONSTRUCTION

ASHLAND BAY

ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/STEM	EXT.	HCWO	NOTES
A	49569	WZC	(1) 75W (M)	6	11	---	---	6.75	4.5	W E0D (18-25W CFL)
B	49570	WZC	(1) 100W (M)	7.5	13.5	---	---	8.25	5.5	W E0D (23-30W CFL)
C	49571	WZC	(1) 150W (M)	8.75	16	---	---	9.5	6	W E0D (30-52W CFL)
D	49668	WZC	(3) 60W (C)	12	21.5	---	---	12.75	7	W
E	49572	WZC	(1) 150W (M)	8.75	17.75	92	28	72	---	D E0D (30-52W CFL) Additional chain 4927 WZC.
F	49667	WZC	(5) 60W (M)	26	20	58	110	36	---	D E0D (13-15W CFL) Additional chain 4927 WZC.
G	49669	WZC	(2) 60W (M) ❖	12	6	---	---	---	---	D
H	49573	WZC	(1) 150W (M)	8.75	19	---	---	---	---	W E0D (30-52W CFL)

Measurements shown in inches. U.S. & Canada Patent Pending.



E | 49572 WZC
Indoor/Outdoor Pendant



F | 49667 WZC
Indoor/Outdoor Chandelier



G | 49669 WZC
Indoor/Outdoor Ceiling



Shown with
Black Post,
9506 BK

H | 49573 WZC
Post Lantern



Harvest Ridge™ Indoor/Outdoor Chandelier 49696 BKT | Page 73

HARVEST RIDGE™

TEXTURED BLACK FINISH WITH
CLEAR RIBBED GLASS INSIDE ETCHED



A | 49691 BKT
Indoor/Outdoor Wall



B | 49692 BKT
Indoor/Outdoor Wall



C | 49693 BKT
Indoor/Outdoor Wall



D | 49696 BKT
Indoor/Outdoor Chandelier



E | 49695 BKT
Indoor/Outdoor Pendant



F | 49694 BKT
Post Lantern


Shown with Black Post, 9506 BK

ALUMINUM
CONSTRUCTION

HARVEST RIDGE™

ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/STEM	EXT.	HCWO	NOTES	
A	49691	BKT	(1) 75W (M)	11	9	---	---	---	11.5	4.25	W E0D (18-25W CFL)
B	49692	BKT	(1) 75W (M)	13	11.25	---	---	---	13.5	5	W E0D (18-25W CFL)
C	49693	BKT	(1) 100W (M)	15	12.5	---	---	---	15.5	6.25	W E0D (23-30W CFL)
D	49696	BKT	(3) 100W (M)	25	7.25	46	110	36	---	---	W Additional stem (12") 2999 BKT.
E	49695	BKT	(1) 100W (M)	13	8.25	47	109	36	---	---	D E0D (23-30W CFL) Additional stem (12") 2999 BKT.
F	49694	BKT	(1) 150W (M)	13	15.5	---	---	---	---	---	W E0D (30-52W CFL)

Measurements shown in inches. U.S. & Canada Patent Pending.



Hatteras Bay™ Indoor/Outdoor Wall 49064 OZ | Page 75

HATTERAS BAY™

OLDE BRONZE® FINISH WITH
CLEAR FRESNEL GLASS



A | 49064 OZ
Indoor/Outdoor Wall

ALUMINUM &
SOLID BRASS
CONSTRUCTION

HATTERAS BAY™

ITEM #	FINISH	INCAND. BULB	W	H	EXT.	HCWO	NOTES
A 49064	OZ	(1) 60W (M)	6.5	8	8.75	3.5	Ⓜ Dark Sky compliant when fresnel lens is installed inward.

Measurements shown in inches. U.S. & Canada Patent Pending.

HATTERAS BAY™

OLDE BRONZE® FINISH WITH
CLEAR FRESNEL GLASS

Hatteras Bay™
is also available
in LED.
See page 33.



A | 49067 OZ
Indoor/Outdoor Wall



B | 49065 OZ
Indoor/Outdoor Wall



Can be converted
to Dark Sky by
installing fresnel
glass inward

ALUMINUM &
SOLID BRASS
CONSTRUCTION

HATTERAS BAY™

	ITEM #	FINISH	INCAND. BULB	W	H	EXT.	HCWO	NOTES
A	49067	OZ	(1) 100W (M)	10.5	10.25	11.75	4	W EOD (23-30W CFL) Dark Sky compliant when fresnel lens is installed inward.
B	49065	OZ	(1) 75W (M)	8.75	9.5	10	3.5	W EOD (9-13W CFL) Dark Sky compliant when fresnel lens is installed inward.

Measurements shown in inches. U.S. & Canada Patent Pending.

CLEAR POINT

BRUSHED ALUMINUM FINISH WITH
WIRE-MESH CLEAR GLASS



A | 49263 BA
Indoor/Outdoor Wall

ALUMINUM
CONSTRUCTION

CLEAR POINT

	ITEM #	FINISH	INCAND. BULB	W	H	EXT.	HCWO	NOTES
A	49263	BA	(1) 75W (M)	11	12.25	4.75	6.38	W

Measurements shown in inches. U.S. & Canada Patent Pending.

HANFORD™

ANVIL IRON FINISH WITH
CLEAR SEEDED GLASS



A | 49006 AVI
Indoor/Outdoor Wall



B | 49007 AVI
Indoor/Outdoor Wall



**VINTAGE
FILAMENT
BULB**

SOLD SEPARATELY
60W Medium Base
4071 CLR

CAST ALUMINUM
CONSTRUCTION

HANFORD™

	ITEM #	FINISH	INCAND. BULB	W	H	EXT.	HCWO	NOTES
A	49006	AVI	(1) 60W (M)	7.5	14.5	6.75	11.25	Ⓜ Ⓜ0D (13-15W CFL)
B	49007	AVI	(1) 100W (M)	9.5	18	8.5	13.5	Ⓜ Ⓜ0D (23-30W CFL)

Measurements shown in inches. U.S. & Canada Patent Pending.

RUSTIC™

RUSTIC™ FINISH OVER SOLID BRASS WITH
CLEAR BEVELED GLASS PANELS



A | 9760 RST
Outdoor Wall



B | 9761 RST
Outdoor Wall



C | 9762 RST
Outdoor Wall

RUSTIC™

	ITEM #	FINISH	INCAND. BULB	W	H	EXT.	HCWO	NOTES
A	9760	RST	(1) 100W (M)	7	13.25	7.75	5.5	W 300 (23-30W CFL)
B	9761	RST	(1) 150W (M)	9.5	17.75	10.5	7	W 300 (23-30W CFL)
C	9762	RST	(1) 150W (M)	11	20.25	11.75	8	W 300 (23-30W CFL)

Measurements shown in inches.



D | 9759 RST
Outdoor Wall



E | 9870 RST
Outdoor Pendant



Shown with
Black Post
9506 BK

F | 9962 RST
Post Lantern

RUSTIC™

SOLID BRASS
CONSTRUCTION

ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/STEM	EXT.	HCWO	NOTES
D	9759	RST	(1) 100W (M)	6	10	---	---	6.75	2.5	Ⓜ Ⓜ0D (23-30W CFL)
E	9870	RST	(1) 150W (M)	11	17.75	92	29	72	---	Ⓜ Ⓜ0D (23-30W CFL) Additional chain 4927 RST.
F	9962	RST	(1) 150W (M)	9.5	18.5	---	---	---	---	Ⓜ Ⓜ0D (23-30W CFL)

Measurements shown in inches.



Westington™ Indoor/Outdoor Wall 45986 OZ | Page 81

WESTINGTON™

OLDE BRONZE® FINISH WITH GOLD HIGHLIGHTS



A | 49585 OZ
Indoor/Outdoor Wall



B | 49586 OZ
Indoor/Outdoor Wall



C | 49587 OZ
Indoor/Outdoor Pendant



D | 49588 OZ
Indoor/Outdoor Chandelier

ALUMINUM
CONSTRUCTION

WESTINGTON™

	ITEM #	FINISH	INCAND. BULB	W	H	OVRLL.		EXTRA WIRE	CHAIN/STEM	EXT.	HCWO	NOTES
					H	H	L					
A	49585	OZ	(1) 100W (M)	10	8.25	---	---	---	---	10.75	2.75	Ⓜ
B	49586	OZ	(1) 100W (M)	14	10	---	---	---	---	14.5	2.75	Ⓜ
C	49587	OZ	(1) 100W (M)	12	3.75	42	---	67	36	---	---	Ⓜ Additional chain 4927 OZ, additional stem 2999 (12") OZ. Sloped ceiling kit included.
D	49588	OZ	(3) 100W (M)	8	7.25	46	32	60	36	---	---	Ⓜ Additional chain 4927 OZ, additional stem 2999 (12") OZ. Sloped ceiling kit included.

Measurements shown in inches. U.S. & Canada Patent Pending.

SEASIDE™

BLACK, BRUSHED NICKEL, OLDE BRICK®,
OLDE BRONZE® OR WHITE FINISH

COORDINATING CEILING FAN

See the full line of Kichler®
Ceiling Fans in catalog K416
or visit kichler.com.

K | 310131 NI, OZ



MATCHING LANDSCAPE LIGHTING

15438 OZ | Path Light
See the complete line of
Kichler® Landscape Lighting
at LandscapeLighting.com.



A | 9021 BK, NI, OZ
Outdoor Wall



B | 9022 BK, NI,
OB, OZ, WH
Outdoor Wall



C | 9023 BK, NI,
OB, OZ
Outdoor Wall



D | 9142 BK, NI, OZ
Outdoor Wall



E | 11098 NI
Outdoor Wall



F | 11099 NI
Outdoor Wall



G | 9044 NI
Outdoor Wall



H | 2621 NI
Outdoor Pendant



J | 2713 NI, OB
Outdoor Pendant

ALUMINUM
CONSTRUCTION

SEASIDE™

ITEM #	FLUOR. ITEM #	FINISH	INCAND. BULB	FLUOR. BULB	W	H	OVRL. H	STEM TILT	EXTRA WIRE	CHAIN/STEM	EXT.	HCWO	NOTES
A	9021	---	BK, NI, OZ	(1) 60W (M)	---	6	7.5	---	---	---	6.5	2.25	Ⓜ G Type lamp recommended.
B	9022	---	BK, NI, OB, OZ, WH	(1) 100W (M)	---	8	12	---	---	---	9	6	Ⓜ G Type lamp recommended.
C	9023	---	BK, NI, OB, OZ	(1) 150W (M)	---	10.5	14.25	---	---	---	11.75	8.75	Ⓜ G Type lamp recommended.
D	9142	---	BK, NI, OZ	(1) 100W (M)	---	12	16.5	---	---	---	13.5	10.25	Ⓜ
E	---	11098	NI	---	(1) 14W (GU24) Ⓜ Ⓜ	8	12	---	---	---	9	6	Ⓜ PBCFA14 decorative bulb incl.
F	---	11099	NI	---	(1) 14W (GU24) Ⓜ Ⓜ	10.5	14.25	---	---	---	11.75	9	Ⓜ PBCFA14 decorative bulb incl.
G	9044	---	NI	(1) 150W (M)	---	11	8	---	---	---	11.5	2.5	Ⓜ Ⓜ G Type lamp recommended.
H	2621	---	NI	(1) 100W (M)	---	8	9.75	48	45°	68	36	---	Ⓜ Ⓜ (18-25W CFL) Add. stem 2999 (12") NI and/or 2997 (24") NI, G Type lamp rec.
J	2713	---	NI, OB	(1) 150W (M) A21 / G40	---	16	13.25	88	---	36	72	---	Ⓜ
K	310131	---	NI, OZ	---	---	---	---	---	---	---	---	---	Ⓜ Ⓜ See the full line of Kichler® Ceiling Fan Catalog K416 or visit kichler.com.

Measurements shown in inches. U.S. Design Patent No. D382,079: A; U.S. Design Patent No. D383,239: B; U.S. & Canada Patent Pending: C, D, G, H, J.

RIPLEY™

OLDE BRONZE® FINISH



A | 49061 OZ
Indoor/Outdoor Wall



B | 49060 OZ
Indoor/Outdoor Wall



C | 49059 OZ
Indoor/Outdoor Wall



Shown with
Architectural Bronze
Post 9506 AZ

D | 49063 OZ
Post Lantern




E | 49062 OZ
Indoor/Outdoor Pendant

RIPLEY™

ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/STEM	EXT.	HCWO	NOTES
A	49061	OZ	(1) 40W (M)	12	10	---	---	13	3.25	Ⓜ Ⓞ Dark sky compliant with use of R14, 40W bulb.
B	49060	OZ	(1) 40W (M)	10	9	---	---	11.25	3	Ⓜ Ⓞ Dark sky compliant with use of R14, 40W bulb.
C	49059	OZ	(1) 40W (M)	8	7.5	---	---	9.25	2.5	Ⓜ Ⓞ Dark sky compliant with use of R14, 40W bulb.
D	49063	OZ	(1) 40W (M)	12	16	---	---	---	---	Ⓜ Ⓞ Dark sky compliant with use of R14, 40W bulb.
E	49062	OZ	(1) 40W (M)	10	8	46	107	36	---	Ⓜ Ⓞ Dark sky compliant with use of R14, 40W bulb. Additional chain 4927 OZ, additional stem 2999 (12") OZ. Sloped ceiling kit included.

Measurements shown in inches. U.S. & Canada Patent Pending.



BRIDGE POINT™

WEATHER ZINC FINISH WITH
CLEAR SEEDED GLASS



A | 49627 WZC
Outdoor Wall



B | 49628 WZC
Outdoor Wall



C | 49629 WZC
Outdoor Wall



D | 49630 WZC
Outdoor Wall



E | 49632 WZC
Outdoor Pendant



F | 49631 WZC
Post Lantern

Shown with
Weathered Zinc
Post, 9506 WZC

BRIDGE POINT™

ALUMINUM
CONSTRUCTION

	ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/STEM	EXT.	HCWO	NOTES
A	49627	WZC	(1) 100W (M)	7	13.25	---	---	---	8.25	7.5	W EOD
B	49628	WZC	(1) 100W (M)	9	16	---	---	---	10.25	8.75	W EOD
C	49629	WZC	(1) 100W (M)	11	20	---	---	---	12.25	10.75	W EOD
D	49630	WZC	(1) 100W (M)	14	26.25	---	---	---	15.25	15.25	W EOD
E	49632	WZC	(1) 100W (M)	11	16	90	34	72	---	8.75	D EOD
F	49631	WZC	(1) 100W (M)	11	21.25	---	---	---	---	---	W EOD

Measurements shown in inches. U.S. & Canada Patent Pending.

PEBBLE LANE

OLDE BRONZE® FINISH WITH
SATIN ETCHED CASED OPAL GLASS



A | 49681 OZ
Outdoor Wall



B | 49682 OZ
Outdoor Wall



C | 49683 OZ
Outdoor Wall



D | 49685 OZ
Outdoor Pendant



Shown with
Olde Bronze®
Post, 9506 OZ

E | 49684 OZ
Post Lantern

ALUMINUM
CONSTRUCTION

PEBBLE LANE

	ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/STEM	EXT.	HCWO	NOTES
A	49681	OZ	(1) 75W (M)	6.5	12.75	---	---	---	7.75	4.25	W EOD
B	49682	OZ	(1) 100W (M)	8	15.5	---	---	---	9.25	4.75	W EOD
C	49683	OZ	(1) 150 (M)	9.5	18.5	---	---	---	10.75	5.25	W EOD
D	49685	OZ	(1) 150 (M)	9.5	17.75	90	33	72	---	---	D EOD Additional chain 4927 OZ.
E	49684	OZ	(1) 150 (M)	9.5	20.5	---	---	---	---	---	W EOD

Measurements shown in inches. U.S. & Canada Patent Pending.



Woodhollow Lane 49675 OZ Outdoor Wall | Page 89

WOODHOLLOW LANE

OLDE BRONZE® FINISH WITH
GOLD HIGHLIGHTS & CLEAR SEEDED GLASS



A | 49676 OZ
Outdoor Wall



B | 49675 OZ
Outdoor Wall



C | 49674 OZ
Outdoor Wall



D | 49678 OZ
Outdoor Pendant



Shown with
Olde Bronze® Post
9595 OZ

E | 49677 OZ
Post Lantern

CAST ALUMINUM
CONSTRUCTION

WOODHOLLOW LANE

ITEM #	FINISH	INCAND. BULB	W	H	OVRLL. H	EXTRA WIRE	CHAIN/STEM	EXT.	HCWO	NOTES	
A	49676	OZ	(1) 75W (M)	10	13	---	---	---	11.25	4.25	W EOD
B	49675	OZ	(1) 75W (M)	8.5	11.5	---	---	---	9.75	4.25	W EOD
C	49674	OZ	(1) 75W (M)	7	9.5	---	---	---	8	3.25	W EOD
D	49678	OZ	(1) 100W (M)	10	12.5	87	35	72	---	---	D EOD Additional chain 4927 OZ.
E	49677	OZ	(1) 75W (M)	10	14.5	---	---	---	---	---	W EOD

Measurements shown in inches. U.S. & Canada Patent Pending.

SUMNER COURT

WEATHERED ZINC FINISH WITH
ETCHED SEEDED GLASS



A | 49660 WZC
Outdoor Wall



B | 49661 WZC
Outdoor Wall



C | 49662 WZC
Outdoor Wall

SUMNER COURT

	ITEM #	FINISH	INCAND. BULB	W	H	EXT.	HCWO	NOTES
A	49660	WZC	(1) 75W (M)	7	11.75	8	5	W 30D (18-25W CFL)
B	49661	WZC	(1) 100W (M)	9	15	10	5	W 30D (23-30W CFL)
C	49662	WZC	(1) 150W (M)	11.75	18.25	12.75	6.5	W 30D (30-52W CFL)

Measurements shown in inches. U.S. & Canada Patent Pending.



D | 49663 WZC
Outdoor Pendant



Shown with
Weathered Zinc
Post, 9506 WZC

E | 49664 WZC
Post Lantern

SUMNER COURT

CAST ALUMINUM
CONSTRUCTION

ITEM #	FINISH	INCAND. BULB	W	H	OVRLL. H	EXTRA WIRE	CHAIN/STEM	NOTES
D	WZC	(1) 150W (M)	11.75	20.75	95	29	72	Ⓟ 30-52W CFL Additional chain 4927 WZC.
E	WZC	(1) 150W (M)	11.75	21	---	---	---	Ⓟ 30-52W CFL

Measurements shown in inches. U.S. & Canada Patent Pending.

CATERHAM™

OLDE BRONZE® FINISH WITH
SATIN ETCHED CASED OPAL GLASS



A | 49642 OZ
49642 OZFL
Indoor/Outdoor Wall



B | 49643 OZ
49643 OZFL
Indoor/Outdoor Wall



C | 49644 OZ
49644 OZFL
Indoor/Outdoor Wall

CAST ALUMINUM
CONSTRUCTION

CATERHAM™

ITEM #	FLOUR. ITEM #	FINISH	INCAND. BULB	FLOUR. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/STEM	EXT.	HCWO	NOTES
A	49642 OZFL	OZ	(1) 100W (M)	(1) 18W GU24 (18)	6.5	11.75	---	---	---	7.5	4	W E0D (23-30W CFL) Indoor/Outdoor.
B	49643 OZFL	OZ	(1) 100W (M)	(1) 18W GU24 (18)	8	14.75	---	---	---	9	4	W E0D (23-30W CFL) Indoor/Outdoor.
C	49644 OZFL	OZ	(1) 150W (M)	(1) 26W GU24 (18)	10	17.5	---	---	---	10.75	4.5	W E0D (30-52W CFL) Indoor/Outdoor.
D	---	OZ	(1) 100W (M)	---	6.5	16	48	58	36	---	---	D E0D (23-30W CFL) Add. chain 4927 OZ, add. stem 2999 (12") OZ. Height includes one 6" stem. Indoor/Outdoor. Sloped ceiling kit incl.
E	49641	---	OZ	(3) 100W (M)	---	14.75	8.75	---	---	---	---	D E0D (23-30W CFL) Indoor/Outdoor.
F	49638	---	OZ	(4) 100W (M)	---	21	12.75	51	67	36	---	D E0D (23-30W CFL) Add. chain 4927 OZ, add. stem 2999 (12") OZ, Indoor/Outdoor. Sloped ceiling kit incl.
G	49646	---	OZ	(1) 100W (M)	---	10	16.75	---	---	---	---	W E0D (23-30W CFL)

Measurements shown in inches. U.S. & Canada Patent Pending.



D | 49640 OZ
Indoor/Outdoor Pendant



E | 49641 OZ
Indoor/Outdoor Ceiling



F | 49638 OZ
Indoor/Outdoor Chandelier



Shown with
Olde Bronze®
Post 9506 OZ

G | 49646 OZ
Post Lantern



Stonebrook Outdoor Wall 49258 AZ | Page 95

STONEBROOK

ARCHITECTURAL BRONZE™ FINISH WITH
SATIN ETCHED CASED OPAL GLASS



A | 49257 AZ
49257 AZFL
Outdoor Wall



B | 49258 AZ
49258 AZFL
Outdoor Wall

STONEBROOK

ALUMINUM
CONSTRUCTION

	ITEM #	FLOUR. ITEM #	FINISH	INCAND. BULB	FLUOR. BULB	W	H	EXT.	HCWO	NOTES
A	49257	49257 AZFL	AZ	(1) 100W (M)	(1) 18W (GU24)	6.5	17.75	8.75	6.75	OD (23-30W CFL)
B	49258	49258 AZFL	AZ	(1) 150W (M)	(1) 26W (GU24)	8.5	23.25	11	8.75	OD (30-52W CFL)

Measurements shown in inches. U.S. & Canada Patent Pending.



Alameda™ Indoor/Outdoor Chandelier 49091 CV | Page 98

ALAMEDA™

CANYON VIEW™ FINISH OVER
SOLID BRASS WITH HONEY
OPALESCENT ART GLASS PANELS



A | 9649 CV
Indoor/Outdoor Wall



B | 9651 CV
Indoor/Outdoor Wall



C | 9652 CV
Indoor/Outdoor Wall



D | 9148 CV
Indoor/Outdoor Wall

ALAMEDA™

ITEM #	FINISH	INCAND. BULB	W	H	EXT.	HCWO	NOTES
A	CV	(1) 75W (M) ✓	5	7	5.75	4	Ⓜ Ⓜ0D (18-25W CFL)
B	CV	(1) 100W (M)	7	11.5	8.5	3	Ⓜ Ⓜ0D (23-30W CFL) Dark Sky compliant with panel inserts 4812 WH. Indoor/Outdoor.
C	CV	(1) 150W (M)	9	14.25	10.45	3.5	Ⓜ Ⓜ0D (23-30W CFL)
D	CV	(1) 150W (M)	7	15	8.5	3	Ⓜ Ⓜ0D (18-25W CFL) Indoor/Outdoor.

Measurements shown in inches.

ALAMEDA™

CANYON VIEW™ FINISH OVER
SOLID BRASS WITH HONEY
OPALESCENT ART GLASS PANELS



A | 49091 CV
Indoor/Outdoor Chandelier



B | 9825 CV
Indoor/Outdoor Ceiling



C | 9849 CV
Indoor/Outdoor Pendant



Shown with
Olde Bronze®
Post 9595 OZ

D | 9953 CV
Post Lantern

ALAMEDA™

SOLID BRASS
CONSTRUCTION

ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/STEM	NOTES
A	49091 CV	(4) 100W (M)	25	17	55	59	36	ⓓ Additional chain 2996 CV or 4927 CV, additional stem 2999 (12") CV. Indoor/Outdoor. Sloped ceiling kit included.
B	9825 CV	(2) 75W (M) ✦	11.5	6.25	---	---	---	ⓓ Ⓜ0D (18-25W CFL) Indoor/Outdoor.
C	9849 CV	(1) 100W (M)	7	11	86	28	72	ⓓ Ⓜ0D (23-30W CFL) Additional chain 4927 CV. Indoor/Outdoor.
D	9953 CV	(1) 150W (M)	9	12.25	---	---	---	Ⓜ Ⓜ0D (23-30W CFL) Converts from post to column mount.

Measurements shown in inches.

SORIA™

AGED BRONZE FINISH WITH
VETRO MICA GLASS



A | 49449 AGZ
Outdoor Wall



B | 49450 AGZ
Outdoor Wall



C | 49451 AGZ
Outdoor Wall

CAST ALUMINUM
CONSTRUCTION

SORIA™

ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/STEM	EXT.	HCWO	NOTES	
A	49449	AGZ	(1) 75W (M)	6	10.25	---	---	---	7	2.25	W EOD (18-25W CFL)
B	49450	AGZ	(1) 100W (M)	7.5	11.75	---	---	---	8.5	2.25	W EOD (23-30W CFL)
C	49451	AGZ	(1) 150W (M)	9	15.25	---	---	---	10	2.75	W EOD (30-52W CFL)
D	49452	AGZ	(1) 100W (M)	9	14	88	28	72	---	---	D EOD (23-30W CFL) Additional chain 4927 AGZ.
E	49153	AGZVM	(2) 60W (C) ♦	9.5	5.25	---	---	---	---	---	D
F	49453	AGZ	(1) 150W (M)	9	16	---	---	---	---	---	W EOD (30-52W CFL)

Measurements shown in inches.



D | 49452 AGZ
Outdoor Pendant



E | 49153 AGZVM
Outdoor Ceiling



Shown with Aged
Bronze Post 9595 AGZ

F | 49453 AGZ
Post Lantern

CAMERON™

PRAIRIE ROCK™ FINISH WITH
WHITE ETCHED LINEN GLASS



A | 9718 PR
11017 PR
Outdoor Wall



















B | 9719 PR
11018 PR
Outdoor Wall



C | 9720 PR
11019 PR
Outdoor Wall

CAST ALUMINUM
CONSTRUCTION

CAMERON™

ITEM #	FLUOR. ITEM #	FINISH	INCAND. BULB	FLUOR. BULB	W	H	OVRLL. H	EXTRA WIRE	CHAIN/STEM	EXT.	HCWO	NOTES	
A	9718	11017	PR	(1) 60W (M)	(1) 13W (GU24)  	6	10.75	---	---	---	7	3	 30D (13-15W CFL)
B	9719	11018	PR	(1) 150W (M)	(1) 18W (GU24)  	8	14.25	---	---	---	9.25	3.75	 30D (23-30W CFL)
C	9720	11019	PR	(1) 200W (M)	(1) 18W (GU24)  	10	17.5	---	---	---	11.25	4.5	 30D (23-30W CFL)
D	9721	---	PR	(1) 150W (M)	---	12	20.5	---	---	---	13.25	4.5	 30D (23-30W CFL)
E	9511	---	PR	(1) 200W (M)	---	10	17.75	92	57	72	---	---	 30D (23-30W CFL) Additional chain 2996 PR.
F	9811	---	PR	(3) 40W (C) 	---	13	6.75	---	---	---	---	---	
G	9902	11020	PR	(1) 150W (M)	(1) 18W (GU24)  	10	20	---	---	---	---	---	 30D (23-30W CFL)

Measurements shown in inches.



D | 9721 PR
Outdoor Wall



E | 9511 PR
Outdoor Pendant



F | 9811 PR
Outdoor Ceiling



Shown with Black Post 9506 BK

G | 9902 PR
11020 PR
Post Lantern

PORTMAN SQUARE™

OLDE BRONZE® FINISH OVER SOLID BRASS WITH ETCHED SEEDED GLASS



A | 49157 OZ
49157 OZFL
Outdoor Wall



B | 49158 OZ
49158 OZFL
Outdoor Wall



C | 49159 OZ
49159 OZFL
Outdoor Wall

SOLID BRASS
CONSTRUCTION

PORTMAN SQUARE™

ITEM #	FLOUR. ITEM #	FINISH	INCAND. BULB	FLOUR. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/STEM	EXT.	HCWO	NOTES
A	49157	49157 OZFL	OZ	(1) 100W (M) ; (1) 18W GU24 (12)	6	8	---	---	---	6.5	4	W EOD (23-30W CFL)
B	49158	49158 OZFL	OZ	(1) 100W (M) ; (1) 18W GU24 (12)	7	10.75	---	---	---	7.75	5.25	W EOD (23-30W CFL)
C	49159	49159 OZFL	OZ	(1) 150W (M) ; (1) 26W GU24 (12)	9	14	---	---	---	9.5	7.25	W EOD (30-52W CFL)
D	49161	---	OZ	(1) 100W (M)	11	18.5	93	25	72	---	---	D EOD (23-30W CFL) Additional chain 4927 OZ.
E	49164	---	OZ	(2) 60W (M)	12	5	---	---	---	---	---	D EOD (13-15W CFL)
F	49160	49160 OZFL	OZ	(2) 100W (M) ; (1) 18W GU24 (12)	11	22	---	---	---	6.25	10	W EOD (23-30W CFL)
G	49162	---	OZ	(1) 100W (M)	9	16.25	---	---	---	---	---	W EOD (23-30W CFL)

Measurements shown in inches. U.S. & Canada Patent Pending.



D | 49161 OZ
Outdoor Pendant



E | 49164 OZ
Outdoor Ceiling



F | 49160 OZ
49160 OZFL
Outdoor Wall



Shown with
Olde Bronze®
Post 9595 OZ

G | 49162 OZ
Post Lantern

CROSS CREEK™

AGED BRONZE FINISH WITH
TEXTURED LINEN SEEDED GLASS



A | 9128 AGZ
Outdoor Wall



B | 9129 AGZ
Outdoor Wall



C | 9130 AGZ
Outdoor Wall



D | 9830 AGZ
Outdoor Ceiling



Shown with
Architectural Bronze
Post 9505 AZ

E | 9529 AGZ
Post Lantern

CAST ALUMINUM
CONSTRUCTION

CROSS CREEK™

ITEM #	FINISH	INCAND. BULB	W	H	EXT.	HCWO	NOTES
A	AGZ	(1) 100W (M)	6	8.5	7.25	2.5	W E0D (9-13W CFL)
B	AGZ	(1) 150W (M)	7.5	13.5	8.75	3	W E0D (23-30W CFL)
C	AGZ	(1) 150W (M)	9	15.75	10.25	3	W E0D (23-30W CFL)
D	AGZ	(2) 75W (M) ♦	9	5.75	---	---	D E0D (18-25W CFL)
E	AGZ	(1) 150W (M)	11.5	17	---	---	W E0D (23-30W CFL)

Measurements shown in inches.

MATCHING LANDSCAPE LIGHTING

15322 AGZ | Path Light
See the complete line of
Kichler® Landscape Lighting
at LandscapeLighting.com



TOWN LIGHT

OLDE BRONZE® FINISH WITH
OUTSIDE ETCHED CLEAR GLASS



A | 49619 OZ
Outdoor Wall



B | 49618 OZ
Outdoor Wall



C | 49620 OZ
Outdoor Wall



D | 49621 OZ
Post Lantern

CAST ALUMINUM
CONSTRUCTION

TOWN LIGHT

ITEM #	FINISH	INCAND. BULB	W	H	EXT.	HCWO	NOTES
A	OZ	(1) 100W (M)	7.75	13.5	8.75	4.5	Ⓜ ⓂⓂⓂ (23-30W CFL)
B	OZ	(1) 60W (M)	6	10.75	7	3.5	Ⓜ ⓂⓂⓂ (13-15W CFL)
C	OZ	(1) 100W (M)	9.75	17	10.75	4.5	Ⓜ ⓂⓂⓂ (23-30W CFL)
D	OZ	(1) 100W (M)	9.75	18	---	---	Ⓜ ⓂⓂⓂ (23-30W CFL)

Measurements shown in inches. U.S. & Canada Patent Pending.

MORRIS™

DISTRESSED COPPER FINISH WITH
INSIDE ETCHED IRIDIZED SEEDED GLASS



A | 9024 DCO
Outdoor Wall



B | 9025 DCO
Outdoor Wall



C | 9027 DCO
Outdoor Wall

MORRIS™

CAST ALUMINUM
CONSTRUCTION

ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/STEM	EXT.	HCWO	NOTES
A	9024	DCO	(1) 60W (M)	6.5	8.25	---	---	7.25	2.75	W
B	9025	DCO	(1) 100W (M)	8	9.5	---	---	8.75	2.75	W
C	9027	DCO	(1) 200W (M)	12	13.5	---	---	13	4.5	W 30D (23-30W CFL)
D	9837	DCO	(1) 150W (M)	12	12.75	87	28	72	---	D 30D (23-30W CFL) Additional chain 4927 DCO.
E	9838	DCO	(2) 60W (M) ❖	11.75	6	---	---	---	---	D 30D (13-15W CFL)
F	9031	DCO	(1) 100W (M)	8	15.25	---	---	8.75	6	W 30D (23-30W CFL)
G	9920	DCO	(1) 200W (M)	12	15	---	---	---	---	W 30D (23-30W CFL)

Measurements shown in inches. U.S. & Canada Patent Pending, A,C,D,E,F,G; U.S. Design Patent No.: D570, 525, B.



D | 9837 DCO
Outdoor Pendant



E | 9838 DCO
Outdoor Ceiling



F | 9031 DCO
Outdoor Wall



G | 9920 DCO
Post Lantern

Shown with Black
Post 9506 BK

BRADFORD

OLDE BRONZE® FINISH WITH
CLEAR SEEDED GLASS



A | 49381 OZ
Indoor/Outdoor Wall



B | 49394 OZ
Indoor/Outdoor Pendant



C | 49382 OZ
Indoor/Outdoor Wall



D | 49383 OZ
Indoor/Outdoor Wall

BRADFORD

ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/STEM	EXT.	HCWO	NOTES	
A	49381	OZ	(1) 75W (M)	6	8.75	---	---	---	7.5	2.75	W E0D (18-25W CFL)
B	49394	OZ	(1) 75W (M)	6	9.25	84	37	72	---	---	D E0D (18-25W CFL) Additional chain 4927 OZ.
C	49382	OZ	(1) 100W (M)	7.25	10.5	---	---	---	9	3.25	W E0D (23-30W CFL)
D	49383	OZ	(1) 150W (M)	8.75	13.5	---	---	---	10.5	3.75	W E0D (30-52W CFL)

Measurements shown in inches. U.S. & Canada Patent Pending.

HALLERON™

LONDONDERRY™ FINISH WITH
CLEAR SEEDED GLASS



A | 49601 LD
Indoor/Outdoor Wall



B | 49600 LD
Indoor/Outdoor Wall



C | 49602 LD
Indoor/Outdoor Ceiling



D | 49603 LD
Indoor/Outdoor Pendant



Shown with
Post 9542 LD

E | 49604 LD
Outdoor Post

CAST ALUMINUM
CONSTRUCTION

HALLERON™

ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/STEM	EXT.	HCWO	NOTES
A	LD	(3) 60W (C)	12	22.75	---	---	---	14.75	13.25	W
B	LD	(2) 60W (C)	10	19	---	---	---	12.5	11	W
C	LD	(3) 40W (C) ❖	12	8.75	---	---	---	---	---	D
D	LD	(3) 60W (C)	12	18.5	93	23	72	---	---	D Additional chain 4927 LD.
E	LD	(3) 60W (C)	12	20.25	---	---	---	---	---	W

Measurements shown in inches. U.S. & Canada Patent Pending.

HARBOR ROW™

OLDE BRONZE® FINISH WITH GOLD HIGHLIGHTS
& CLEAR SEEDED GLASS



A | 49714 OZ
Indoor/Outdoor Wall



B | 49715 OZ
Indoor/Outdoor Wall



C | 49716 OZ
Indoor/Outdoor Wall



D | 49717 OZ
Indoor/Outdoor Pendant



Shown with Olde Bronze® Post 9506 OZ

E | 49718 OZ
Post Lantern

CAST ALUMINUM
CONSTRUCTION

HARBOR ROW™

	ITEM #	FINISH	INCAND. BULB	W	H	OVRLL. H	EXTRA WIRE	CHAIN/STEM	EXT.	HCWO	NOTES
A	49714	OZ	(2) 60W (C)	8.25	18.5	---	---	---	7.75	12	W
B	49715	OZ	(3) 60W (C)	10.5	23.25	---	---	---	8	12.25	W
C	49716	OZ	(4) 60W (M)	12.5	28.75	---	---	---	9.25	13.75	W
D	49717	OZ	(4) 60W (C)	10.5	27.25	---	---	---	---	---	D Additional chain 4927 OZ.
E	49718	OZ	(4) 60W (C)	10.5	25.75	100	14	72	---	---	W

Measurements shown in inches. U.S. & Canada Patent Pending.

NORTHVIEW™

WEATHERED ZINC FINISH WITH
ETCHED SEEDED GLASS



A | 49700 WZC
Outdoor Wall



B | 49701 WZC
Outdoor Wall



C | 49702 WZC
Outdoor Wall



D | 49703 WZC
Outdoor Wall

NORTHVIEW™

ITEM #	FINISH	INCAND. BULB	W	H	EXT.	HCWO	NOTES
A	WZC	(1) 60W (M)	6.5	13.25	8	8.25	W 30D (13-15W CFL)
B	WZC	(1) 75W (M)	8.5	17.25	10.5	11	W 30D (18-25W CFL)
C	WZC	(1) 100W (M)	10.5	27	12.75	15.75	W 30D (23-30W CFL)
D	WZC	(1) 150W (M)	12.5	31.75	14.75	18.25	W 30D (30-52W CFL)

Measurements shown in inches. U.S. & Canada Patent Pending.



E | 49704 WZC
Outdoor Pendant



F | 49705 WZC
Post Lantern

NORTHVIEW™

**ALUMINUM
CONSTRUCTION**

	ITEM #	FINISH	INCAND. BULB	W	H	OVRLL. H	EXTRA WIRE	CHAIN/STEM	NOTES
E	49704	WZC	(1) 150W (M)	8.5	15	89	33	72	Ⓟ 30D (30-52W CFL) Additional chain 4927 WZC.
F	49705	WZC	(1) 150W (M)	8.5	17.5	---	---	---	Ⓟ 30D (30-52W CFL)

Measurements shown in inches. U.S. & Canada Patent Pending.

GALEMORE

OLDE BRONZE® FINISH WITH
CLEAR SEEDED GLASS



A | 49709 OZ
Indoor/Outdoor Wall



B | 49710 OZ
Indoor/Outdoor Wall



C | 49711 OZ
Indoor/Outdoor Wall



D | 49713 OZ
Indoor/Outdoor Pendant



Shown with Olde
Bronze® Post 9506 OZ

E | 49712 OZ
Post Lantern

GALEMORE

ALUMINUM
CONSTRUCTION

	ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/STEM	EXT.	HCWO	NOTES
A	49709	OZ	(2) 60W (C)	6.5	18	---	---	---	6.75	7.5	W
B	49710	OZ	(3) 60W (C)	7.75	21.75	---	---	---	8.25	8.95	W
C	49711	OZ	(3) 60W (C)	9.5	26.5	---	---	---	10	11	W
D	49713	OZ	(3) 60W (C)	9.5	23.75	98	19	72	---	---	D Additional chain 4927 OZ.
E	49712	OZ	(3) 60W (C)	9.5	23	---	---	---	---	---	W

Measurements shown in inches. U.S. & Canada Patent Pending.

PALLERTON WAY™

OLDE BRONZE® FINISH WITH
GOLD HIGHLIGHTS & ETCHED SEEDED GLASS



A | 49579 OZ
Indoor/Outdoor Wall



C | 49581 OZ
Indoor/Outdoor Wall



B | 49580 OZ
Indoor/Outdoor Wall

PALLERTON WAY™

	ITEM #	FINISH	INCAND. BULB	W	H	EXT.	HCWO	NOTES
A	49579	OZ	(1) 75W (M)	5.75	14.25	6.25	9.75	W30D (18-25W CFL)
B	49580	OZ	(1) 100W (M)	7.25	17.5	8.5	6	W30D (23-30W CFL)
C	49581	OZ	(1) 150W (M)	8.5	20.25	10	7	W30D (30-52W CFL)

Measurements shown in inches. U.S. & Canada Patent Pending.



D | 49582 OZ
Indoor/Outdoor Pendant



Shown with
Olde Bronze®
Post 9506 OZ

E | 49583 OZ
Post Lantern

PALLERTON WAY™

CAST ALUMINUM
CONSTRUCTION

	ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/STEM	NOTES
D	49582	OZ	(1) 100W (M)	7.25	17.5	92	30	72	Ⓟ 0D (23-30W CFL) Additional chain 4927 OZ.
E	49583	OZ	(1) 100W (M)	8.5	23	---	---	---	Ⓟ 0D (23-30W CFL)

Measurements shown in inches. U.S. & Canada Patent Pending.

HAYMAN BAY™

OLDE BRONZE® FINISH WITH
GOLD HIGHLIGHTS &
ETCHED SEEDED GLASS



A | 49291 OZ
Indoor/Outdoor Wall

Gold
Highlights



C | 49293 OZ
Indoor/Outdoor Wall



B | 49292 OZ
Indoor/Outdoor Wall

HAYMAN BAY™

	ITEM #	FINISH	INCAND. BULB	W	H	EXT.	HCWO	NOTES
A	49291	OZ	(1) 75W (M)	7	13.25	7.75	4	W E0D (18-25W CFL)
B	49292	OZ	(1) 100W (M)	9	17	9.75	4.75	W E0D (23-30W CFL)
C	49293	OZ	(1) 150W (M)	11	20.75	11.75	6	W E0D (30-52W CFL)

Measurements shown in inches. U.S. & Canada Patent Pending.



D | 49294 OZ
Indoor/Outdoor Pendant



Shown with
Post 9506 OZ

E | 49295 OZ
Post Lantern

HAYMAN BAY™

CAST ALUMINUM
CONSTRUCTION

	ITEM #	FINISH	INCAND. BULB	W	H	OVRLL. H	EXTRA WIRE	CHAIN/STEM	NOTES
D	49294	OZ	(1) 100W (M)	9	19	93	29	72	D E0D (23-30W CFL) Additional chain 4927 OZ.
E	49295	OZ	(1) 100W (M)	9	19.75	---	---	---	W E0D (23-30W CFL)

Measurements shown in inches. U.S. & Canada Patent Pending.

PARK ROW

OLDE BRONZE® FINISH WITH
ETCHED SEEDED GLASS



A | 49611 OZ
Outdoor Wall



B | 49612 OZ
Outdoor Wall



C | 49613 OZ
Outdoor Wall

ALUMINUM
CONSTRUCTION

PARK ROW

ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/STEM	EXT.	HCWO	NOTES	
A	49611	OZ	(1) 60W (M)	6	10	---	---	---	7	4	W 30D (13-15W CFL)
B	49612	OZ	(1) 75W (M)	8	15.5	---	---	---	9	5.25	W 30D (18-25W CFL)
C	49613	OZ	(1) 100W (M)	10	19.5	---	---	---	11	6.5	W 30D (23-30W CFL)
D	49615	OZ	(1) 150W (M)	12	20.5	95	27	72	---	---	D 30D (30-52W CFL) Additional chain 4927 OZ.
E	49616	OZ	(2) 40W (C) ❖	11	6.5	---	---	---	---	---	D
F	49614	OZ	(1) 150W (M)	12	30	---	---	---	14	12.75-17.25	W 30D (30-52W CFL)
G	49617	OZ	(1) 150W (M)	12	23.5	---	---	---	---	---	W 30D (30-52W CFL)

Measurements shown in inches. U.S. & Canada Patent Pending.



D | 49615 OZ
Outdoor Pendant



E | 49616 OZ
Outdoor Ceiling



F | 49614 OZ
Outdoor Wall



G | 49617 OZ
Post Lantern



Tournai™ Post Lantern 9565 BKT | Page 131 & Outdoor Wall 9357 BKT | Page 130

TOURNAI™

LONDONDERRY™ FINISH WITH
CLEAR SEEDED GLASS



Large Scale Lantern
5' 9" Feet Tall

A | 9362 LD
Outdoor Wall

TOURNAI™

ITEM #	FINISH	INCAND. BULB	W	H	L	EXT.	HCWO	NOTES
A 9362**	LD	(5) 100W (M)	25.5	69.5	36.5	36.5	22-42	Ⓜ ⓘ Ⓜ 00 (23-30W CFL) Variable height mounting hardware included. Junction Box 22"-42".

Measurements shown in inches. **Special Order, call for delivery.

TOURNAI™

LONDONDERRY™ FINISH WITH
CLEAR SEEDED GLASS



A | 9355 LD
Outdoor Wall



B | 9356 LD
Outdoor Wall



C | 9357 LD
Outdoor Wall

TOURNAI™

	ITEM #	FINISH	INCAND. BULB	W	H	EXT.	HCWO	NOTES
A	9355	LD	(1) 100W (M)	6	10.5	7.75	4	Ⓜ Ⓢ 0D (23-30W CFL)
B	9356	LD	(1) 150W (M)	7.5	18	11.25	5.75-11.75	Ⓜ ⓘ Ⓢ 0D (23-30W CFL) Variable height mounting hardware included. Junction Box 5.75"-11.75".
C	9357	LD	(2) 60W (C)	10	24	14.75	6-17.5	Ⓜ ⓘ Variable height mounting hardware included. Junction Box 6"-17.5".

Measurements shown in inches.



D | 9358 LD
Outdoor Wall



E | 9359 LD
Outdoor Wall



F | 9360 LD
Outdoor Wall

TOURNAI™

CAST ALUMINUM
CONSTRUCTION

	ITEM #	FINISH	INCAND. BULB	W	H	EXT.	HCWO	NOTES
D	9358	LD	(3) 60W (C)	11.75	29	17.75	6.5-21.5	Ⓜ ⓘ Variable height mounting hardware included. Junction Box 6.5"-21.5".
E	9359	LD	(4) 60W (C)	14	37.75	20.75	11-33.25	Ⓜ ⓘ Variable height mounting hardware included. Junction Box 11"-33.25".
F	9360	LD	(4) 100W (M)	17	46	25	24.5	Ⓜ ⓘ Ⓜ OD (23-30W CFL)

Measurements shown in inches.

TOURNAI™

LONDONDERRY™ FINISH WITH
CLEAR SEEDED GLASS

Large Scale
Hanging Lantern
47.5" Inches Tall



A | 9854 LD
Outdoor Ceiling



B | 9855 LD
Outdoor Pendant



C | 9564 LD
Outdoor Pendant



D | 9568 LD
Outdoor Pendant



Shown with
Londonderry™
Post 9510 LD

E | 9558 LD
Post Lantern



Shown with
Londonderry™
Post 9510 LD

F | 9559 LD
Post Lantern



Shown with
Londonderry™
Post 9523 LD

G | 9565 LD
Post Lantern

TOURNAI™

CAST ALUMINUM
CONSTRUCTION

ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/STEM	NOTES	
A	9854	LD	(2) 60W (C) ✦	12	7.5	---	---	---	Ⓟ
B	9855	LD	(3) 60W (C)	12	24.75	99	21	72	Ⓟ Additional chain 4927 LD.
C	9564	LD	(4) 100W (M)	17	33.5	108	52	72	Ⓟ ⓂⓃⓄ (23-30W CFL) Additional chain 4908 LD.
D	9568	LD	(8) 100W (M)	25.5	47.5	123	46	72	Ⓟ ⓂⓃⓄ (23-30W CFL) Additional chain 4930 LD.
E	9558	LD	(3) 60W (C)	12	27	---	---	---	Ⓜ Requires 3" Post.
F	9559	LD	(4) 60W (C)	14	30	---	---	---	Ⓜ Requires 3" Post.
G	9565	LD	(4) 100W (M)	17	37.5	---	---	---	Ⓜ ⓂⓃⓄ (23-30W CFL) Requires 4" Post.

Measurements shown in inches.

TOURNAI™

TEXTURED BLACK FINISH WITH
CLEAR SEEDED GLASS



Large Scale Lantern
5' 9" tall

A | 9362** BKT
Outdoor Wall
NOT TO SCALE

CAST ALUMINUM
CONSTRUCTION

TOURNAI™

ITEM #	FINISH	INCAND. BULB	W	H	L	EXT.	HCWO	NOTES
A 9362**	BKT	(5) 100W (M)	25.5	69.5	36.5	36.5	36	Ⓜ ⓘ Ⓜ 0D (23-30W CFL) Variable height mounting hardware included. Junction Box 22"-42".

Measurements shown in inches. **Special Order, call for delivery.

TOURNAI™

TEXTURED BLACK FINISH WITH
CLEAR SEEDED GLASS



A | 9355 BKT
Outdoor Wall



B | 9356 BKT
Outdoor Wall



C | 9357 BKT
Outdoor Wall



D | 9358 BKT
Outdoor Wall



E | 9359 BKT
Outdoor Wall



F | 9360 BKT
Outdoor Wall

TOURNAI™

ITEM #	FINISH	INCAND. BULB	W	H	EXT.	HCWO	NOTES
A	9355	BKT (1) 100W (M)	6	10.5	7.75	4	Ⓜ ⓂOD (23-30W CFL)
B	9356	BKT (1) 150W (M)	7.5	18	11.25	---	Ⓜ ⓂOD (23-30W CFL)
C	9357	BKT (2) 60W (C)	10	24	14.75	---	Ⓜ
D	9358	BKT (3) 60W (C)	11.75	29	17.75	6.5-21.5	Ⓜ Ⓜ Variable height mounting hardware included. Junction Box 6.5"-21.5".
E	9359	BKT (4) 60W (C)	14	37.75	20.75	---	Ⓜ
F	9360	BKT (4) 100W (M)	17	46	25	---	Ⓜ ⓂOD (23-30W CFL)

Measurements shown in inches.

Large Scale
Hanging Lantern
47.5" Inches Tall



G | 9568 BKT
Outdoor Pendant



H | 9564 BKT
Outdoor Pendant



J | 9855 BKT
Outdoor Pendant



K | 9854 BKT
Outdoor Ceiling



L | 9565 BKT
Post Lantern

Shown with Textured
Black Post 9523 BKT



M | 9559 BKT
Post Lantern

Shown with Textured
Black Post 9510 BKT



N | 9558 BKT
Post Lantern

Shown with Textured
Black Post 9510 BKT

TOURNAI™

CAST ALUMINUM
CONSTRUCTION

ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/STEM	NOTES
G	9568	BKT (8) 100W (M)	25.5	47.5	123	46	72	Ⓧ 30D (23-30W CFL) Additional chain 4930 BK.
H	9564	BKT (4) 100W (M)	17	33.5	108	52	72	Ⓧ 30D (23-30W CFL) Additional chain 4908 BK.
J	9855	BKT (3) 60W (C)	12	24.75	99	21	72	Ⓧ Additional chain 4927 BK.
K	9854	BKT (2) 60W (C) ❖	12	7.5	---	---	---	Ⓧ
L	9565	BKT (4) 100W (M)	17	37.5	---	---	---	Ⓧ 30D (23-30W CFL) Requires 4" Post.
M	9559	BKT (4) 60W (M)	14	30	---	---	---	Ⓧ Requires 3" Post.
N	9558	BKT (3) 60W (C)	12	27	---	---	---	Ⓧ Requires 3" Post.

Measurements shown in inches.

MOUNT VERNON

OLDE BRONZE® FINISH OVER SOLID BRASS
WITH CLEAR SEEDED GLASS



A | 9707 OZ
Outdoor Wall



B | 9708 OZ
Outdoor Wall



C | 9709 OZ
Outdoor Wall



D | 9704 OZ
Outdoor Wall

MOUNT VERNON

ITEM #	FINISH	INCAND. BULB	W	H	EXTRA WIRE	EXT.	HCWO	NOTES
A	9707	OZ (1) 100W (M)	5.5	12.5	---	6.25	5.5	W EOD (23-30W CFL)
B	9708	OZ (1) 150W (M)	7.5	16.75	---	8.25	6.75	W EOD (23-30W CFL)
C	9709	OZ (1) 150W (M)	9.5	19.5	7.5	10.25	7.25	W EOD (23-30W CFL)
D	9704	OZ (4) 60W (C)	13	27.75	---	13.75	11.25	W

Measurements shown in inches.



E | 9804 OZ
Outdoor Pendant



F | 9809 OZ
Outdoor Pendant

Mount Vernon is also available in LED. See page 32.



G | 9703 OZ
Outdoor Wall



Shown with Olde Bronze® Post 9506 OZ

H | 9909 OZ
Post Lantern

MOUNT VERNON

SOLID BRASS
CONSTRUCTION

	ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	L	EXTRA WIRE	CHAIN/STEM	EXT.	HCWO	NOTES
E	9804	OZ	(4) 60W (C)	13	26	100	---	13	72	---	---	Ⓛ Additional chain 4927 OZ.
F	9809	OZ	(1) 150W (M)	9.5	18.5	57	9.5	64	36	---	---	Ⓛ ⓂOD (23-30W CFL) Additional chain 4927 OZ.
G	9703	OZ	(6) 60W (C)	16	32.5	---	17	---	---	17	12.25	Ⓜ
H	9909	OZ	(1) 150W (M)	9.5	20.75	---	---	---	---	---	---	Ⓜ ⓂOD (23-30W CFL)

Measurements shown in inches.

MOUNT VERNON

BLACK FINISH OVER SOLID BRASS
WITH CLEAR SEEDED GLASS



A | 9707 BK
Outdoor Wall



B | 9708 BK
Outdoor Wall



C | 9709 BK
Outdoor Wall



D | 9704 BK
Outdoor Wall

MOUNT VERNON

ITEM #	FINISH	INCAND. BULB	W	H	EXT.	HCWO	NOTES
A	BK	(1) 100W (M)	5.5	12.5	6.25	5.5	W 30D (23-30W CFL)
B	BK	(1) 150W (M)	7.5	16.75	8.25	6.75	W 30D (23-30W CFL)
C	BK	(1) 150W (M)	9.5	19.5	10.25	7.25	W 30D (23-30W CFL)
D	BK	(4) 60W (C)	13	27.75	13.75	11.25	W

Measurements shown in inches.



E | 9804 BK
Outdoor Pendant



F | 9809 BK
Outdoor Pendant

Mount Vernon is also available in LED. See page 32.



Shown with Black Post 9506 BK

G | 9909 BK
Post Lantern

MOUNT VERNON

SOLID BRASS
CONSTRUCTION

	ITEM #	FINISH	INCAND. BULB	W	H	OVRLL. H	EXTRA WIRE	CHAIN/STEM	NOTES
E	9804	BK	(4) 60W (C)	13	26	100	13	72	Ⓢ Additional chain 4927 BK.
F	9809	BK	(1) 150W (M)	9.5	18.5	57	64	36	Ⓢ Ⓢ0D (23-30W CFL) Additional chain 4927 BK.
G	9909	BK	(1) 150W (M)	9.5	20.75	---	---	---	Ⓢ Ⓢ0D (23-30W CFL)

Measurements shown in inches.

MOUNT VERNON ENERGY EFFICIENT

OLDE BRONZE® FINISH OVER SOLID BRASS
WITH ETCHED SEEDED GLASS



A | 10907 OZ
Outdoor Wall



B | 10908 OZ
Outdoor Wall



Shown with
Olde Bronze®
Post 9506 OZ

C | 10911 OZ
Post Lantern



D | 10909 OZ
Outdoor Wall

MOUNT VERNON ENERGY EFFICIENT

SOLID BRASS
CONSTRUCTION

	FLUOR. ITEM #	FINISH	FLUOR. BULB	W	H	EXT.	HCWO	NOTES
A	10907	OZ	(1) 13W (GU24)	5.5	12.5	6.25	5.25	
B	10908	OZ	(1) 13W (GU24)	7.5	16.75	8.25	7	
C	10911	OZ	(1) 18W (GU24)	9.5	21.25	---	---	
D	10909	OZ	(1) 18W (GU24)	9.5	19.5	10.25	7.25	

Measurements shown in inches.

COURTYARD™ ENERGY EFFICIENT

RUBBED BRONZE™ FINISH WITH
ETCHED SEEDED GLASS



A | 11012 RZ
Outdoor Wall



B | 11011 RZ
Outdoor Wall



C | 11010 RZ
Outdoor Wall



D | 11013 RZ
Outdoor Wall



E | 11016 RZ
Outdoor Pendant



F | 11014 RZ
Post Lantern

Shown with Black
Post 9506 BK

SOLID BRASS
CONSTRUCTION

COURTYARD™ ENERGY EFFICIENT

	FLUOR. ITEM #	FINISH	FLUOR. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/STEM	EXT.	HCWO	NOTES
A	11012	RZ	(1) 18W (GU24)	10.25	22.25	---	---	---	13.5	9	
B	11011	RZ	(1) 18W (GU24)	8.25	17.75	---	---	---	11	7.75	
C	11010	RZ	(1) 13W (GU24)	6.25	11	---	---	---	7	3.5	
D	11013	RZ	(1) 26W (GU24)	12.25	26.5	---	---	---	16.5	12.5	
E	11016	RZ	(1) 26W (GU24)	12.25	21.5	96	20	72	---	---	Additional chain 4927 RZ.
F	11014	RZ	(1) 18W (GU24)	10.25	23.75	---	---	---	---	---	

Measurements shown in inches.

COURTYARD™

RUBBED BRONZE™ FINISH WITH
CLEAR SEEDED GLASS



A | 9032 RZ
Outdoor Wall



B | 9033 RZ
Outdoor Wall



C | 9034 RZ
Outdoor Wall



D | 9035 RZ
Outdoor Wall

COURTYARD™

ITEM #	FINISH	INCAND. BULB	W	H	EXT.	HCWO	NOTES	
A	9032	RZ	(1) 100W (M)	6.25	11	7	3.5	Ⓜ Ⓜ Ⓜ (23-30W CFL)
B	9033	RZ	(1) 150W (M)	8.25	17.75	11	7.75	Ⓜ Ⓜ Ⓜ (23-30W CFL)
C	9034	RZ	(3) 60W (C)	10.5	22.25	13.5	9	Ⓜ
D	9035	RZ	(3) 60W (M)	12.25	26.5	16.5	12.5	Ⓜ

Measurements shown in inches.



E | 9060 RZ
Outdoor Wall



F | 9538 RZ
Outdoor Ceiling



G | 9539 RZ
Outdoor Pendant



Shown with
Black Post
9595 OZ

H | 9532 RZ
Post Lantern



Shown with
Black Post
9595 OZ

J | 9533 RZ
Post Lantern

CAST ALUMINUM
CONSTRUCTION

COURTYARD™

ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/STEM	EXT.	HCWO	NOTES
E	9060	RZ (3) 100W (M)	13.5	40.5	---	65	---	18	20	W ⓘ 30D (23-30W CFL) Variable height mounting hardware included. Junction Box 18"-24".
F	9538	RZ (3) 40W (C) ✓	12.25	6.25	---	---	---	---	---	D
G	9539	RZ (3) 60W (M)	12.25	21.5	96	19	72	---	---	D Additional chain 4927 RZ.
H	9532	RZ (1) 200W (M)	10.25	23.75	---	---	---	---	---	W ⓘ 30D (30-52W CFL)
J	9533	RZ (3) 60W (C)	12.25	27	---	---	---	---	---	W

Measurements shown in inches.

COURTYARD™

TEXTURED BLACK FINISH WITH
CLEAR SEEDED GLASS



A | 9032 BKT
Outdoor Wall



B | 9033 BKT
Outdoor Wall



C | 9034 BKT
Outdoor Wall



D | 9035 BKT
Outdoor Wall

COURTYARD™

ITEM #	FINISH	INCAND. BULB	W	H	EXT.	HCWO	NOTES	
A	9032	BKT	(1) 100W (M)	6.25	11	7	3.5	Ⓜ ⓂⓂⓂⓂ (23-30W CFL)
B	9033	BKT	(1) 150W (M)	8.25	17.75	11	7.75	Ⓜ ⓂⓂⓂⓂ (23-30W CFL)
C	9034	BKT	(3) 60W (C)	10.5	22.25	13.5	9	Ⓜ
D	9035	BKT	(3) 60W (M)	12.25	26.5	16.5	12.5	Ⓜ

Measurements shown in inches.



E | 9060 BKT
Outdoor Wall



F | 9538 BKT
Outdoor Ceiling



G | 9539 BKT
Outdoor Pendant



Shown with
Black Post
9595 BK

H | 9532 BKT
Post Lantern



Shown with
Black Post
9595 BK

J | 9533 BKT
Post Lantern

CAST ALUMINUM
CONSTRUCTION

COURTYARD™

ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/STEM	EXT.	HCWO	NOTES
E	9060	BKT (3) 100W (M)	13.5	40.5	---	65	---	18	20	W ① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨ ⑩ ⑪ ⑫ ⑬ ⑭ ⑮ ⑯ ⑰ ⑱ ⑲ ⑳ ㉑ ㉒ ㉓ ㉔ ㉕ ㉖ ㉗ ㉘ ㉙ ㉚ ㉛ ㉜ ㉝ ㉞ ㉟ ㊱ ㊲ ㊳ ㊴ ㊵ ㊶ ㊷ ㊸ ㊹ ㊺ ㊻ ㊼ ㊽ ㊾ ㊿ ① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨ ⑩ ⑪ ⑫ ⑬ ⑭ ⑮ ⑯ ⑰ ⑱ ⑲ ⑳ ㉑ ㉒ ㉓ ㉔ ㉕ ㉖ ㉗ ㉘ ㉙ ㉚ ㉛ ㉜ ㉝ ㉞ ㉟ ㊱ ㊲ ㊳ ㊴ ㊵ ㊶ ㊷ ㊸ ㊹ ㊺ ㊻ ㊼ ㊽ ㊾ ㊿
F	9538	BKT (3) 40W (C) ✓	12.25	6.25	---	---	---	---	---	D
G	9539	BKT (3) 60W (M)	12.25	21.5	96	19	72	---	---	D Additional chain 4927 BK.
H	9532	BKT (1) 200W (M)	10.25	23.75	---	---	---	---	---	W ① ② ③ ④ ⑤ ⑥ ⑦ ⑧ ⑨ ⑩ ⑪ ⑫ ⑬ ⑭ ⑮ ⑯ ⑰ ⑱ ⑲ ⑳ ㉑ ㉒ ㉓ ㉔ ㉕ ㉖ ㉗ ㉘ ㉙ ㉚ ㉛ ㉜ ㉝ ㉞ ㉟ ㊱ ㊲ ㊳ ㊴ ㊵ ㊶ ㊷ ㊸ ㊹ ㊺ ㊻ ㊼ ㊽ ㊾ ㊿
J	9533	BKT (3) 60W (C)	12.25	27	---	---	---	---	---	W

Measurements shown in inches.

SALISBURY™

RUBBED BRONZE™ FINISH WITH
WHITE LINEN GLASS



A | 9039 RZ
11001 RZ
Outdoor Wall



B | 9040 RZ
11002 RZ
Outdoor Wall



C | 9041 RZ
Outdoor Wall



D | 9042 RZ
Outdoor Wall



E | 9043 RZ
Outdoor Wall

SALISBURY™

ITEM #	FLUOR. ITEM #	FINISH	INCAND. BULB	FLUOR. BULB	W	H	EXT.	HCWO	NOTES
A	9039	---	(1) 60W (M)	---	6	10.5	7	3.5	W 30D (13-15W CFL)
A	---	11001	---	(1) 13W (GU24)	6	10.25	7	4.5	W 30D (13-15W CFL)
B	9040	---	(1) 100W (M)	---	8	19.25	10.75	7	W 30D (23-30W CFL)
B	---	11002	---	(1) 18W (GU24)	8	19.5	10.75	6.75	W
C	9041	---	(1) 100W (M)	---	8	19.25	10.75	9.25	W 30D (23-30W CFL)
D	9042	---	(1) 150W (M)	---	10	24.25	13.25	12.25	W 30D (23-30W CFL)
E	9043	---	(1) 200W (M)	---	12	29.25	16.25	14.25	W 30D (23-30W CFL)

Measurements shown in inches.



F | 9843 RZ
Outdoor Pendant



G | 9848 RZ
Outdoor Ceiling



Shown with
Architectural Bronze™
Post 9506 AZ

H | 9938 RZ
Post Lantern



Shown with
Architectural Bronze™
Post 9506 AZ

J | 9940 RZ
Post Lantern

CAST ALUMINUM
CONSTRUCTION

SALISBURY™

	ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/STEM	NOTES
F	9843	RZ	(1) 200W (M)	12	25	99	22	72	Ⓛ 30D (23-30W CFL) Add. chain 4927 RZ.
G	9848	RZ	(2) 60W (M)	13.5	7.5	---	---	---	Ⓛ 30D (13-15W CFL)
H	9938	RZ	(1) 150W (M)	10	22	---	---	---	Ⓜ 30D (23-30W CFL)
J	9940	RZ	(1) 200W (M)	12	25.5	---	---	---	Ⓜ 30D (23-30W CFL)

Measurements shown in inches.

SALISBURY™

BLACK FINISH WITH WHITE LINEN GLASS



A | 9039 BK
Outdoor Wall



B | 9040 BK
Outdoor Wall



C | 9041 BK
Outdoor Wall



D | 9042 BK
Outdoor Wall



E | 9043 BK
Outdoor Wall

SALISBURY™

ITEM #	FINISH	INCAND. BULB	W	H	EXT.	HCWO	NOTES
A	BK	(1) 60W (M)	6	10.5	7	3.5	W EOD (13-15W CFL)
B	BK	(1) 100W (M)	8	19.25	10.75	7	W EOD (23-30W CFL)
C	BK	(1) 100W (M)	8	19.25	10.75	9.25	W EOD (23-30W CFL)
D	BK	(1) 150W (M)	10	24.25	13.25	12.25	W EOD (23-30W CFL)
E	BK	(1) 200W (M)	12	29	16.25	14.25	W EOD (23-30W CFL)

Measurements shown in inches.



F | 9843 BK
Outdoor Pendant



G | 9848 BK
Outdoor Ceiling



Shown with Black Post 9506 BK

H | 9938 BK
Post Lantern



Shown with Black Post 9506 BK

J | 9940 BK
Post Lantern

CAST ALUMINUM
CONSTRUCTION

SALISBURY™

	ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/STEM	NOTES
F	9843	BK	(1) 200W (M)	12	25	99	22	72	Ⓧ 30D (23-30W CFL) Additional chain 4927 BK.
G	9848	BK	(2) 60W (M)	13.5	7.5	---	---	---	Ⓧ 30D (13-15W CFL)
H	9938	BK	(1) 150W (M)	10	21.75	---	---	---	Ⓧ 30D (23-30W CFL)
J	9940	BK	(1) 200W (M)	12	25.5	---	---	---	Ⓧ 30D (23-30W CFL)

Measurements shown in inches.

SAUSALITO™

OLDE BRONZE® FINISH WITH
CLEAR RIBBED OPTIC GLASS



A | 9492 OZ
Outdoor Wall



C | 9412 OZ
Outdoor Wall



B | 9452 OZ
Outdoor Wall

SAUSALITO™

	ITEM #	FINISH	INCAND. BULB	W	H	EXT.	HCWO		NOTES
A	9492	OZ	(3) 60W (C)	11	28	13.5	10.5	W	
B	9452	OZ	(3) 60W (C)	9.5	24	12	10	W	
C	9412	OZ	(1) 100W (M)	7	19.5	9	7.5	W	LED (23-30W CFL)

Measurements shown in inches.



D | 9832 OZ
Outdoor Pendant



Shown with
Olde Bronze™
Post 9506 OZ

E | 9932 OZ
Post Lantern

SAUSALITO™

ALUMINUM
CONSTRUCTION

	ITEM #	FINISH	INCAND. BULB	W	H	OVRLL. H	EXTRA WIRE	CHAIN/STEM	NOTES
D	9832	OZ	(3) 60W (C)	11.5	23	97	15	72	Ⓟ Additional chain 4927 OZ.
E	9932	OZ	(3) 60W (C)	11.5	24.5	---	---	---	Ⓜ

Measurements shown in inches.

GROVE MILL™

LIFEBRITE™ POLISHED BRASS FINISH OVER SOLID BRASS WITH CLEAR BEVELED GLASS PANELS



A | 9409 PB
Outdoor Wall



B | 9439 PB
Outdoor Wall



C | 9489 PB
Outdoor Wall



D | 9889 PB
Outdoor Pendant



E | 9989 PB
Post Lantern

Shown with Black Post 9506 BK

SOLID BRASS WITH
LifeBrite™
BY KICHLER®

Kichler's LifeBrite™ Finish has a lifetime finish guarantee to withstand the harshest elements, salt air and extreme weather conditions.

GROVE MILL™

ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/STEM	EXT.	HCWO	NOTES
A	PB	(1) 100W (M)	7.5	12.25	---	---	---	7	3.25	W E20D (23-30W CFL)
B	PB	(2) 60W (C)	9.5	20	---	---	---	9.5	10	W
C	PB	(3) 60W (C)	11.25	23.75	---	---	---	11.25	11.75	W
D	PB	(3) 60W (C)	11.5	21.5	96	16	72	---	---	D
E	PB	(3) 60W (C)	9.75	25.25	---	---	---	---	---	W

Measurements shown in inches.

BAY SHORE™

LIFEBRITE™ POLISHED BRASS FINISH OVER SOLID BRASS WITH CLEAR BEVELED GLASS PANELS



A | 9712 PB
Outdoor Wall



B | 9711 PB
Outdoor Wall



Shown with Black Post 9506 BK

C | 9913 PB
Post Lantern



D | 9713 PB
Outdoor Wall

SOLID BRASS WITH **LifeBrite™** BY KICHLER®

Kichler's LifeBrite™ Finish has a lifetime finish guarantee to withstand the harshest elements, salt air and extreme weather conditions.

BAY SHORE™

	ITEM #	FINISH	INCAND. BULB	W	H	EXT.	HCWO	NOTES
A	9712	PB	(1) 100W (M)	7	15.5	7.75	12	Ⓜ Ⓜ Ⓜ (23-30W CFL)
B	9711	PB	(1) 100W (M)	5.75	10.25	6.75	4	Ⓜ Ⓜ Ⓜ (23-30W CFL)
C	9913	PB	(1) 100W (M)	9.5	22.5	---	---	Ⓜ Ⓜ Ⓜ (23-30W CFL)
D	9713	PB	(1) 100W (M)	9.5	20	10.75	15.5	Ⓜ Ⓜ Ⓜ (23-30W CFL)

Measurements shown in inches.



Manningham™ Post Light 49388 OZ, Outdoor Ceiling 49389 OZ | Page 153 & Outdoor Wall 49384 OZ | Page 151

MANNINGHAM™

OLDE BRONZE® FINISH WITH
CLEAR SEEDED GLASS



A | 49384 OZ
Indoor/Outdoor Wall

MANNINGHAM™

	ITEM #	FINISH	INCAND. BULB	W	H	EXT.	HCWO	NOTES
A	49384	OZ	(1) 75W (M)	5	10.75	5	6	W 00 (18-25W CFL)

Measurements shown in inches. U.S. & Canada Patent Pending.

MANNINGHAM™

OLDE BRONZE® FINISH WITH
CLEAR SEEDED GLASS



A | 49385 OZ
Indoor/Outdoor Wall



B | 49386 OZ
Indoor/Outdoor Wall

MANNINGHAM™

	ITEM #	FINISH	INCAND. BULB	W	H	EXT.	HCWO	NOTES
A	49385	OZ	(2) 60W (C)	7.5	18.75	10	12	Ⓜ
B	49386	OZ	(3) 60W (C)	9	22.25	11	14.5	Ⓜ

Measurements shown in inches. U.S. & Canada Patent Pending.



C | 49387 OZ
Indoor/Outdoor Pendant



D | 49389 OZ
Indoor/Outdoor Ceiling



Shown with
Olde Bronze®
Post, 9506 OZ

E | 49388 OZ
Post Lantern

MANNINGHAM™

CAST ALUMINUM
CONSTRUCTION

	ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/STEM	NOTES
C	49387	OZ	(3) 60W (C)	8.5	19	93	14	72	Ⓧ Additional chain 4927 OZ.
D	49389	OZ	(2) 75W (M) Ⓧ	11.75	5	---	---	---	Ⓧ 800 (18-25W CFL)
E	49388	OZ	(3) 60W (C)	8.5	21	---	---	---	Ⓧ

Measurements shown in inches. U.S. & Canada Patent Pending.



Wiscombe Park™ Outdoor Wall 49502 WZC | Page 158 & Outdoor Wall 49501 WZC | Page 159

WISCOMBE PARK™

OLDE BRONZE® FINISH WITH
GOLD HIGHLIGHTS WITH CLEAR SEEDED GLASS



A | 49502 OZ
Outdoor Wall

WISCOMBE PARK™

CAST ALUMINUM
CONSTRUCTION

ITEM #	FINISH	INCAND. BULB	W	H	EXT.	HCWO	NOTES
A 49502	OZ	(3) 60W (C)	7.5	21.75	9.75	13.25	W

Measurements shown in inches. U.S. & Canada Patent Pending.

WISCOMBE PARK™

OLDE BRONZE® FINISH WITH
GOLD HIGHLIGHTS WITH CLEAR SEEDED GLASS



A | 49503 OZ
Outdoor Wall



B | 49504 OZ
Outdoor Wall

CAST ALUMINUM
CONSTRUCTION

WISCOMBE PARK™

	ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/ STEM	EXT.	HCWO	NOTES
A	49503	OZ	(4) 60W (C)	9	26.25	---	---	---	11.5	15.75	W
B	49504	OZ	(4) 60W (C)	11	30.5	---	---	---	13.5	18.25	W
C	49501	OZ	(1) 100W (M)	6	12.25	---	---	---	6.5	7.5	W LED (23-30W CFL)
D	49505	OZ	(4) 60W (C)	11	23	97	10	72	---	---	D Additional Chain 4927 OZ.
E	49506	OZ	(4) 60W (C)	9	23.25	---	---	---	---	---	W

Measurements shown in inches. U.S. & Canada Patent Pending.



C | 49501 OZ
Outdoor Wall



D | 49505 OZ
Outdoor Pendant



Shown with Olde
Bronze® Post 9506 OZ

E | 49506 OZ
Post Lantern

WISCOMBE PARK™

WEATHERED ZINC® FINISH WITH
CLEAR SEEDED GLASS



A | 49502 WZC
Outdoor Wall



C | 49504 WZC
Outdoor Wall



B | 49503 WZC
Outdoor Wall

CAST ALUMINUM
CONSTRUCTION

WISCOMBE PARK™

ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/STEM	EXT.	HCWO	NOTES	
A	49502	WZC	(3) 60W (C)	7.5	21.75	---	---	---	9.75	13.25	W
B	49503	WZC	(4) 60W (C)	9	26.25	---	---	---	11.5	15.75	W
C	49504	WZC	(4) 60W (C)	11	30.5	---	---	---	13.5	18.25	W
D	49501	WZC	(1) 100W (M)	6	12.25	---	---	---	6.5	7.5	W LED (23-30W CFL)
E	49505	WZC	(4) 60W (C)	11	23	97	10	72	---	---	D Additional chain 4927 WZC.
F	49506	WZC	(4) 60W (C)	9	23.25	---	---	---	---	---	W
G	49277	WZC	(2) 75W (M)	11.5	5.5	---	---	---	---	---	D LED (13-15W CFL)

Measurements shown in inches. U.S. & Canada Patent Pending.



D | 49501 WZC
Outdoor Wall



E | 49505 WZC
Outdoor Pendant



Shown with Black
Post 9506 BK

F | 49506 WZC
Post Lantern



G | 49277 WCZ
Outdoor Ceiling

VENETIAN RAIN

BRUSHED BRONZE FINISH WITH
VERTICAL RAIN GLASS



A | 49131 BRZ
Outdoor Wall



B | 49132 BRZ
Outdoor Wall



C | 49135 BRZ
Outdoor Wall

VENETIAN RAIN

CAST ALUMINUM
CONSTRUCTION

ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/STEM	EXT.	HCWO	NOTES	
A	49131	BRZ	(2) 60W (C)	7.25	25.25	---	---	---	10.5	6	Ⓜ
B	49132	BRZ	(3) 60W (C)	9.25	31	---	---	---	13.5	7	Ⓜ
C	49135	BRZ	(4) 60W (C) ❖	11.25	37	---	---	---	16	9	Ⓜ
D	49130	BRZ	(1) 60W (C) ✓	6.75	11.75	---	---	---	3.75	7.25	Ⓜ Ⓞ
E	49136	BRZ	(2) 40W (C) ❖	9.25	5.5	---	---	---	---	---	Ⓧ
F	49134	BRZ	(2) 60W (C)	7.25	24.75	98.75	16	72	---	---	Ⓧ Additional chain 4927 BRZ.
G	49133	BRZ	(3) 60W (C)	9.25	32.5	---	---	---	15.5	---	Ⓜ

Measurements shown in inches. U.S. & Canada Patent Pending.



D | 49130 BRZ
Outdoor Wall
ADA Compliant



E | 49136 BRZ
Outdoor Ceiling



F | 49134 BRZ
Outdoor Pendant

Shown with
Architectural Bronze™
Post 9506 AZ



G | 49133 BRZ
Post Lantern

VENETIAN RAIN

BLACK FINISH AND GOLD HIGHLIGHTS
WITH VERTICAL RAIN GLASS



A | 49131 BKG
Outdoor Wall



B | 49132 BKG
Outdoor Wall



C | 49135 BKG
Outdoor Wall

VENETIAN RAIN

CAST ALUMINUM
CONSTRUCTION

ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/STEM	EXT.	HCWO	NOTES
A	49131	BKG (2) 60W (C)	7.25	25.25	---	---	---	10.5	6	Ⓜ
B	49132	BKG (3) 60W (C)	9.25	31	---	---	---	13.5	7	Ⓜ
C	49135	BKG (4) 60W (C) ❖	11.25	37	---	---	---	16	9	Ⓜ
D	49130	BKG (1) 60W (C) ✓	6.75	11.75	---	---	---	3.75	7.25	Ⓜ Ⓞ
E	49136	BKG (2) 40W (C) ❖	9.25	5.5	---	---	---	---	---	Ⓧ
F	49134	BKG (2) 60W (C)	7.25	24.75	98.75	16	72	---	---	Ⓧ Additional chain 4927 BKG.
G	49133	BKG (3) 60W (C)	9.25	32.5	---	---	---	15.5	---	Ⓜ

Measurements shown in inches. U.S. & Canada Patent Pending.



D | 49130 BKG
Outdoor Wall
ADA Compliant



E | 49136 BKG
Outdoor Ceiling



F | 49134 BKG
Outdoor Pendant

Shown with Black
Post 9506 BK



G | 49133 BKG
Post Lantern

TOLERAND™

TEXTURED BLACK FINISH WITH
CLEAR SEEDED GLASS



A | 49552 BKT
Outdoor Wall



B | 49553 BKT
Outdoor Wall



C | 49554 BKT
Outdoor Wall



VINTAGE
FILAMENT
BULB

SOLD SEPARATELY
60W Medium Base
4071 CLR



D | 49556 BKT
Outdoor Pendant



E | 49555 BKT
Post Lantern

Shown with
Black Post 9506 BK

TOLERAND™

CAST ALUMINUM
CONSTRUCTION

	ITEM #	FINISH	INCAND. BULB	W	H	OVRLL. H	EXTRA WIRE	CHAIN/STEM	EXT.	HCWO	NOTES
A	49552	BKT	(1) 75W (M)	5.75	12	---	---	---	6.5	3.75	W E0D (18-25W CFL)
B	49553	BKT	(1) 100W (M)	7.75	17.75	---	---	---	8.5	6.5	W E0D (23-30W CFL)
C	49554	BKT	(1) 150W (M)	9.5	20.25	---	---	---	10.25	7.25	W E0D (30-52W CFL)
D	49556	BKT	(1) 150W (M)	9.5	19.75	94	28	72	---	---	D E0D (30-52W CFL) Additional chain 4927 BK.
E	49555	BKT	(1) 150W (M)	9.5	21.75	---	---	---	---	---	W E0D (30-52W CFL)

Measurements shown in inches. U.S. & Canada Patent Pending.

SAVANNAH ESTATES™

OLDE BRONZE® FINISH OVER SOLID BRASS WITH CLEAR BEVELED GLASS



A | 9676 OZ
Outdoor Wall



B | 9677 OZ
Outdoor Wall



C | 9631 OZ
Outdoor Wall



D | 9931 OZ
Post Lantern

Shown with
Olde Bronze®
Post 9510 OZ



E | 9831 OZ
Outdoor Pendant

SAVANNAH ESTATES™

SOLID BRASS
CONSTRUCTION

	ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/STEM	EXT.	HCWO	NOTES
A	9676	OZ	(2) 60W (C)	9.5	19.25	---	---	---	9	10	W
B	9677	OZ	(3) 60W (C)	12	24.75	---	---	---	11.5	12	W
C	9631	OZ	(4) 60W (C)	13	35	---	---	---	16	18-25.5	W ⓘ Variable height mounting hardware included. Junction Box 18-25.5".
D	9931	OZ	(3) 60W (C)	12.25	25	---	---	---	---	---	W
E	9831	OZ	(4) 60W (C)	15	30.25	105	12	72	---	---	ⓓ Additional chain 4927 OZ.

Measurements shown in inches.

EAU CLAIRE™

OLDE BRONZE® FINISH WITH
ANTIQUE CLEAR GLASS



A | 9347 OZ
Outdoor Wall



B | 9348 OZ
Outdoor Wall

EAU CLAIRE™

ALUMINUM
CONSTRUCTION

	ITEM #	FINISH	INCAND. BULB	W	H	EXT.	HCWO	NOTES
A	9347	OZ	(1) 150W (M)	9	18.25	12.75	10.25	Ⓜ Ⓜ0D (23-30W CFL)
B	9348	OZ	(3) 60W (C)	11	32	15	12.75-20	Ⓜ ⓘ Variable height mounting hardware included. Junction Box 12.75"-20".

Measurements shown in inches.

TURLEE™

BLACK FINISH WITH
SATIN ETCHED GLASS



A | 49654 BK
Outdoor Wall



B | 49655 BK
Outdoor Wall



C | 49656 BK
Outdoor Wall



D | 49657 BK
Post Lantern



E | 49658 BK
Outdoor Pendant



F | 9886 BKS
Outdoor Ceiling

TURLEE™

ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/STEM	EXT.	HCWO	NOTES
A	49654	BK	(1) 100W (M)	6	11	---	---	7.25	3.5	W EOD (18-25 CFL)
B	49655	BK	(1) 100W (M)	8	14.25	---	---	9.25	3.5	W EOD (18-25 CFL)
C	49656	BK	(1) 100W (M)	9.5	17.25	---	---	10.75	4.5	W EOD (18-25 CFL)
D	49657	BK	(1) 100W (M)	9.5	20.5	---	---	---	---	W EOD (30-52 CFL)
E	49658	BK	(1) 100W (M)	9.5	16	89	69	72	---	D EOD (30-52 CFL) Additional chain 4927 BK.
F	9886	BKS	(2) 40W (C) ❖	12	7	---	---	---	---	D EOD

Measurements shown in inches. U.S. & Canada Patent Pending.

TURLEE™

OLDE BRONZE® FINISH
WITH SATIN ETCHED GLASS



A | 49656 OZ
Outdoor Wall



B | 49655 OZ
Outdoor Wall



C | 49654 OZ
Outdoor Wall



D | 9886 OZS
Outdoor Ceiling



E | 49658 OZ
Outdoor Pendant



F | 49657 OZ
Post Lantern

TURLEE™

CAST ALUMINUM
CONSTRUCTION

ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/STEM	EXT.	HCWO	NOTES
A	49656	OZ	(1) 100W (M)	9.5	17.25	---	---	10.75	4.5	W 30D (18-25 CFL)
B	49655	OZ	(1) 100W (M)	8	14.25	---	---	9.25	3.5	W 30D (18-25 CFL)
C	49654	OZ	(1) 100W (M)	6	11	---	---	7.25	3.5	W 30D (18-25 CFL)
D	9886	OZS	(2) 40W (C) ❖	12	7	---	---	---	---	D 30D
E	49658	OZ	(1) 100W (M)	9.5	16	89	69	72	---	D 30D (30-52 CFL) Additional chain 4927 OZ.
F	49657	OZ	(1) 100W (M)	9.5	20.5	---	---	---	---	W 30D (30-52 CFL)

Measurements shown in inches. U.S. & Canada Patent Pending.

CHESAPEAKE™

BLACK OR TANNERY BRONZE™ FINISH WITH
CLEAR BEVELED GLASS PANELS



A | 9774 BK
Outdoor Wall



B | 9776 BK
Outdoor Wall



C | 9777 BK
Outdoor Wall



D | 49255 BK, TZ
Outdoor Wall



E | 9886 BK, TZ
Outdoor Ceiling

Shown with Tannery
Bronze™ Post 9506 TZ



F | 49256 BK, TZ
Post Lantern

CHESAPEAKE™

ITEM #	FINISH	INCAND. BULB	W	H	EXT.	HCWO	NOTES	
A	9774	BK	(1) 60W (M)	5.5	10.25	6.25	2.25	W 30D (23-30W CFL)
B	9776	BK	(1) 100W (M)	6.5	11.75	8	3.25	W 30D (23-30W CFL)
C	9777	BK	(3) 60W (C)	7.25	14.75	8.5	3.5	W
D	49255	BK, TZ	(1) 100W (M)	6.5	17	7.75	14	W 30D (23-30W CFL)
E	9886	BK, TZ	(2) 40W (C) ❖	12	7	---	---	D
F	49256	BK, TZ	(1) 100W (M)	6.5	18	---	---	W 30D (23-30W CFL)

Measurements shown in inches.

CHESAPEAKE™

BLACK FINISH WITH
SATIN ETCHED GLASS PANELS



A | 9776 BKS
Outdoor Wall



B | 9774 BKS
Outdoor Wall



C | 49256 BKS
Post Lantern

Shown with Black
Post 9506 BK



D | 9886 BKS
Outdoor Ceiling



E | 49255 BKS
Outdoor Wall

CHESAPEAKE™

CAST ALUMINUM
CONSTRUCTION

	ITEM #	FINISH	INCAND. BULB	W	H	EXT.	HCWO	NOTES
A	9776	BKS	(1) 100W (M)	6.5	11.75	8	3.25	W EOD (23-30W CFL)
B	9774	BKS	(1) 60W (M)	5.5	10.25	6.25	2.25	W EOD (23-30W CFL)
C	49256	BKS	(1) 100W (M)	6.5	18	---	---	W EOD (23-30W CFL)
D	9886	BKS	(2) 40W (C) ❖	12	7	---	---	D
E	49255	BKS	(1) 100W (M)	6.5	17	7.75	14	W EOD (23-30W CFL)

Measurements shown in inches.

CHESAPEAKE™

WHITE FINISH WITH CLEAR
BEVELED GLASS PANELS



A | 9774 WH
Outdoor Wall



B | 9776 WH
Outdoor Wall



C | 9777 WH
Outdoor Wall



D | 49255 WH
Outdoor Wall

Shown with White
Post 9501 WH



E | 49256 WH
Post Lantern



F | 9322 WH
Outdoor Ceiling

CHESAPEAKE™

ITEM #	FINISH	INCAND. BULB	W	H	EXT.	HCWO	NOTES	
A	9774	WH	(1) 60W (M)	5.5	10.25	6.25	2.25	W EOD (23-30W CFL)
B	9776	WH	(1) 100W (M)	6.5	11.75	8	3.25	W EOD (23-30W CFL)
C	9777	WH	(3) 60W (C)	7.25	14.75	8.5	3.5	W
D	49255	WH	(1) 100W (M)	6.5	17	7.75	14	W EOD (23-30W CFL)
E	49256	WH	(1) 100W (M)	6.5	18	---	---	W EOD (23-30W CFL)
F	9322	WH	(2) 60W (M)	10.5	5.5	---	---	D EOD

Measurements shown in inches.

EMBASSY ROW

OLDE BRONZE® FINISH OVER SOLID BRASS WITH CLEAR BEVELED GLASS PANELS



A | 9785 OZ
Outdoor Wall



B | 9784 OZ
Outdoor Wall



C | 9783 OZ
Outdoor Wall



D | 9985 OZ
Post Lantern

Shown with
Olde Bronze®
Post 9510 OZ



E | 9885 OZ
Outdoor Pendant

EMBASSY ROW

SOLID BRASS
CONSTRUCTION

ITEM #	FINISH	INCAND. BULB	W	H	OVRLL. H	EXTRA WIRE	CHAIN/STEM	EXT.	HCWO	NOTES
A	9785	OZ	(3) 60W (C)	10.5	21	---	---	9.75	8.25	W
B	9784	OZ	(1) 100W (M)	8.25	14.75	---	---	8	5.5	W E30D (23-30W CFL)
C	9783	OZ	(1) 100W (M)	7	10.75	---	---	7	4	W E30D (23-30W CFL)
D	9985	OZ	(3) 60W (C)	10.5	20.75	---	---	---	---	W
E	9885	OZ	(3) 60W (C)	10.5	19.5	94	14	72	---	D Additional chain 4927 OZ.

Measurements shown in inches.

KIRKWOOD™

TANNERY BRONZE™ FINISH
WITH SEEDED GLASS



A | 9028 TZ
Outdoor Wall



B | 9029 TZ
Outdoor Wall



C | 9030 TZ
Outdoor Wall



D | 9859 TZ
Outdoor Ceiling



E | 9810 TZ
Outdoor Pendant

Shown with
Tannery Bronze™
Post 9506 TZ



F | 9918 TZ
Post Lantern

KIRKWOOD™

CAST ALUMINUM
CONSTRUCTION

ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/STEM	EXT.	HCWO	NOTES	
A	9028	TZ	(1) 100W (M)	6.5	13	---	8	---	7.5	8	W 30D (23-30W CFL)
B	9029	TZ	(1) 150W (M)	8.5	17	---	10.25	---	9.5	10.25	W 30D (23-30W CFL)
C	9030	TZ	(3) 60W (C)	9.75	21	---	---	---	11.5	13	W
D	9859	TZ	(1) 100W (M) ✓	7.25	7.25	---	---	---	---	---	D 30D (9-13W CFL)
E	9810	TZ	(1) 150W (M)	8.5	18	92	22	72	---	---	D 30D (23-30W CFL) Additional chain 4927 TZ.
F	9918	TZ	(3) 60W (C)	9.75	23.5	---	---	---	---	---	W

Measurements shown in inches.

KIRKWOOD™

BLACK FINISH WITH SEEDED GLASS



A | 9030 BK
Outdoor Wall



B | 9029 BK
Outdoor Wall



C | 9028 BK
Outdoor Wall



D | 9918 BK
Post Lantern

Shown with Black Post 9506 BK



E | 9810 BK
Outdoor Pendant



F | 9859 BK
Outdoor Ceiling

KIRKWOOD™

CAST ALUMINUM
CONSTRUCTION

ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/STEM	EXT.	HCWO	NOTES
A	9030	BK	(3) 60W (C)	9.75	21	---	---	11.5	13	W
B	9029	BK	(1) 150W (M)	8.5	17	---	10.25	9.5	10.25	W 30D (23-30W CFL)
C	9028	BK	(1) 100W (M)	6.5	13	---	8	7.5	8	W 30D (23-30W CFL)
D	9918	BK	(3) 60W (C)	9.75	23.5	---	---	---	---	W
E	9810	BK	(1) 150W (M)	8.5	18	92	22	72	---	D 30D (23-30W CFL) Additional chain 4927 BK.
F	9859	BK	(1) 100W (M) ✓	7.25	7.25	---	---	---	---	D 30D (9-13W CLF)

Measurements shown in inches.

TOWNHOUSE™

BLACK OR TANNERY BRONZE™ FINISH WITH
CLEAR CURVED BEVELED GLASS PANELS



A | 9788 BK, TZ
Outdoor Wall



B | 9789 BK, TZ
Outdoor Wall



C | 9790 BK, TZ
Outdoor Wall



D | 9791 BK, TZ
Outdoor Wall



E | 49185 BK, TZ
Outdoor Wall



F | 9892 BK, TZ
Outdoor Pendant



G | 9886 BK, TZ
Outdoor Ceiling



H | 9992 BK, TZ
Post Lantern

TOWNHOUSE™

CAST ALUMINUM
CONSTRUCTION

ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/STEM	EXT.	HCWO	NOTES	
A	9788	BK, TZ	(1) 100W (M)	6.5	11.75	---	---	---	6.5	2.75	W 30D (23-30W CFL)
B	9789	BK, TZ	(1) 100W (M)	7.25	15.25	---	---	---	9	4.5	W 30D (23-30W CFL)
C	9790	BK, TZ	(1) 100W (M)	7.25	21.5	---	---	---	9.75	16.75	W 30D (23-30W CFL)
D	9791	BK, TZ	(1) 100W (M)	9.25	26.75	---	---	---	10.25	21	W 30D (23-30W CFL)
E	49185	BK, TZ	(3) 60W (C)	12.25	31	---	---	---	12.25	25.25	W
F	9892	BK, TZ	(1) 100W (M)	9.25	24.5	99	23	72	---	---	D 30D (23-30W CFL) Additional chain 4927 BK, TZ.
G	9886	BK, TZ	(2) 40W (C) ❖	12	7	---	---	---	---	---	D
H	9992	BK, TZ	(1) 100W (M)	9.25	24.25	---	---	---	---	---	W 30D (23-30W CFL)

Measurements shown in inches.

BK
Black

TZ
Tannery Bronze®

BARRIE

BLACK OR TANNERY BRONZE™ FINISH WITH
CLEAR BEVELED GLASS



A | 9794 BK, TZ
Outdoor Wall



B | 49183 BK, TZ
Outdoor Wall



C | 9735 BK, TZ
Outdoor Wall



D | 49186 BK, TZ
Outdoor Wall



E | 9736 BK, TZ
Outdoor Wall

BARRIE

ITEM #	FINISH	INCAND. BULB	W	H	EXTRA WIRE	EXT.	HCWO	NOTES
A	9794 BK, TZ	(1) 100W (M)	4.75	8.5	2.75	5.75	2.75	Ⓜ Ⓜ Ⓜ (23-30W CFL)
B	49183 BK, TZ	(1) 100W (M)	6.25	10.25	---	6.5	1.75	Ⓜ Ⓜ Ⓜ (23-30W CFL)
C	9735 BK, TZ	(1) 100W (M)	8	15.5	---	8	6.25	Ⓜ Ⓜ Ⓜ (23-30W CFL)
D	49186 BK, TZ	(1) 100W (M)	9.75	19	---	9.5	7.75	Ⓜ Ⓜ Ⓜ (23-30W CFL)
E	9736 BK, TZ	(1) 100W (M)	8	21.75	---	8	15	Ⓜ Ⓜ Ⓜ (23-30W CFL)

Measurements shown in inches.



F | 9835 BK, TZ
Outdoor Pendant



G | 9886 BK, TZ
Outdoor Ceiling



H | 49187 BK, TZ
Post Lantern

Shown with Tannery Bronze™ Post 9595 TZ



J | 9935 BK, TZ
Post Lantern

Shown with Tannery Bronze™ Post 9506 TZ

BARRIE

**CAST ALUMINUM
CONSTRUCTION**

	ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/STEM	NOTES
F	9835	BK, TZ	(1) 100W (M)	8	13.5	88	25	72	Ⓛ 300 (23-30W CFL) Additional chain 4927 BK, TZ.
G	9886	BK, TZ	(2) 40W (C) ❖	12	7	---	---	---	Ⓛ
H	49187	BK, TZ	(1) 100W (M)	9.75	18	---	---	---	Ⓛ 300 (23-30W CFL)
J	9935	BK, TZ	(1) 100W (M)	8	16	---	---	---	Ⓛ 300 (23-30W CFL)

Measurements shown in inches.



MADISON ENERGY EFFICIENT

TANNERY BRONZE™ FINISH WITH
UMBER LINEN GLASS



A | 10950 TZ
Outdoor Wall



B | 10954 TZ
Outdoor Wall



C | 10953 TZ
Outdoor Wall



D | 10956 TZ
Post Lantern

Shown with
Tannery Bronze™
Post 9506 TZ

MADISON ENERGY EFFICIENT

	FLUOR. ITEM #	FINISH	FLUOR. BULB	W	H	EXT.	HCWO	NOTES
A	10950	TZ	(1) 13W (GU24)	8	14.75	8.5	4.25	
B	10954	TZ	(1) 18W (GU24)	9.5	17	10.25	6.5	
C	10953	TZ	(1) 13W (GU24)	8	19.75	8.5	15.5	
D	10956	TZ	(1) 18W (GU24)	9.5	22.75	---	---	

Measurements shown in inches.

MADISON

BLACK, TANNERY BRONZE™ OR WHITE FINISH
WITH CLEAR BEVELED GLASS



A | 9654 BK, TZ, WH
Outdoor Wall



B | 9653 BK, TZ, WH
Outdoor Wall



C | 9655 BK, TZ
Outdoor Wall



D | 9650 BK, TZ, WH
Outdoor Wall



Shown with
Black Post
9506 BK

E | 9956 BK, TZ
Post Lantern



F | 9805 BK, TZ, WH
Outdoor Pendant



G | 9850 BK, TZ
Outdoor Ceiling

MADISON

CAST ALUMINUM
CONSTRUCTION

ITEM #	FINISH	INCAND. BULB	W	H	OVRL. H	EXTRA WIRE	CHAIN/STEM	EXT.	HCWO	NOTES
A	9654 BK, TZ, WH	(1) 150W (M)	9.5	22.75	---	---	---	10	16.5	W EOD (23-30W CFL)
B	9653 BK, TZ, WH	(1) 100W (M)	8	19.5	---	15.5	---	8.5	15.5	W EOD (23-30W CFL)
C	9655 BK, TZ	(1) 100W (M)	9.25	17	---	---	---	10	6	W EOD (23-30W CFL)
D	9650 BK, TZ, WH	(1) 100W (M)	8	14.75	---	---	---	8.5	4.75	W EOD (23-30W CFL)
E	9956 BK, TZ	(1) 150W (M)	9.5	22.75	---	---	---	---	---	W EOD (23-30W CFL)
F	9805 BK, TZ, WH	(1) 100W (M)	9.25	13.5	88	32	72	---	---	D EOD (23-30W CFL) Additional chain 4927 BK, TZ.
G	9850 BK, TZ	(2) 60W (C) ❖	10.75	7.25	---	---	---	---	---	D

Measurements shown in inches.



NEW STREET™

ASSORTED FINISHES & GLASS



A | 9611 BKS
Outdoor Wall



A | 9611 OZS
Outdoor Wall



A | 9611 SSS
Outdoor Wall



A | 9611 TZS
Outdoor Wall



A | 9611 BK
Outdoor Wall



A | 9611 OZ
Outdoor Wall



A | 9611 SS
Outdoor Wall



A | 9611 TZ
Outdoor Wall



A | 9611 WH
Outdoor Wall



B | 9618 OZ
Outdoor Wall



B | 9618 SS
Outdoor Wall

OUTDOOR CEILING

ASSORTED FINISHES & GLASS



C | 9322 BK
Outdoor Ceiling



C | 9322 WH
Outdoor Ceiling



D | 365 BK
Outdoor Ceiling



D | 365 TZ
Outdoor Ceiling



E | 9320 BK
Outdoor Ceiling



E | 9320 WH
Outdoor Ceiling



F | 345 BK
Outdoor Ceiling



F | 345 TZ
Outdoor Ceiling



G | 9859 BK
Outdoor Ceiling



G | 9859 TZ
Outdoor Ceiling



H | 9817 AP
Outdoor Ceiling



J | 11028 BK, WH
Outdoor Ceiling

CAST ALUMINUM CONSTRUCTION

NEW STREET™ AND OUTDOOR CEILING

ITEM #	FLUOR. ITEM #	FINISH	FLUOR. BULB	INCAND. BULB	W	H	EXT.	HCWO	NOTES
A	9611	BK, BKS, OZ, OZS, SS, SSS, TZ, TZS, WH	---	(1) 60W (M)	5	8.25	5.75	3	W E30D (23-30W CFL) Aluminum construction.
B	9618	OZ, SS	---	(1) 100W (M)	5.5	10.25	5.75	3.25	W E30D (23-30W CFL) OZ: Solid Brass Construction, SS: Stainless Steel Construction.
C	9322	BK, WH	---	(2) 60W (M) ✓	10.5	5.5	---	---	D Etched White Acrylic Panels.
D	365	BK, TZ	---	(1) 60W (M) ❖	7.5	5	---	---	D E30D (9-13W CFL) Textured Clear Glass.
E	9320	BK, WH	---	(1) 60W (M)	8.5	5	---	---	D Etched White Acrylic Panels.
F	345	BK, TZ	---	(2) 60W (M) ❖	9.25	5.25	---	---	D E30D (9-13W CFL) Textured Clear Glass.
G	9859	BK, TZ	---	(1) 100W (M) ✓	7.25	7.25	---	---	D E30D (9-13W CFL) Seeded Glass.
H	9817	AP	---	(2) 100W (M) ✓	13	7	---	---	D E30D (18-25W CFL) AP: Satin Etched Glass.
J	---	11028	BK, WH	(1) 18W (GU24) E E17 E17	11.25	4.75	---	---	W Etched Acrylic Panels.

Measurements shown in inches. U.S. & Canada Patent Pending: H.



OUTDOOR WALL & ENERGY EFFICIENT

ASSORTED FINISHES



A | 9095 AZ
10922 AZ
Outdoor Wall



B | 49110 AVI
49110 AVIFL
Leeds™ Outdoor Wall



C | 10941 BK
Outdoor Wall



D | 49577 BKTP
Outdoor Wall



E | 10923 BK, TZ
Outdoor Wall



F | 10622 BK, WH
Outdoor Wall



G | 6052 AZ, WH
Outdoor Wall



H | 6051 AZ, WH
Outdoor Wall



J | 1148 BK, TZ, WH
Outdoor Wall

OUTDOOR WALL

ITEM #	FLUOR. ITEM #	FINISH	INCAND. BULB	FLUOR. BULB	W	H	EXT.	HCWO	NOTES	
A	9095 10922	AZ	(1) 100W (M)	(1) 13W (GU24)	7	12	5.5	6	Dark Sky Panels included.	
B	49110	49110 AVIFL	AVI	(1) 100W (M)	(2) 18W (GU24)	5.75	12.25	5	6	(13-15W CFL)
C	---	10941	BK	---	(1) 18W (GU24)	7.75	9.75	4.25	4.25	
D	49577	---	BKTP	(1) 75W (M)	---	4.5	7.25	5.75	2.25	(30-52W CFL)
E	---	10923	BK, TZ	---	(1) 13W (GU24)	4.75	9	5.75	2.5	Satin Etched Glass.
F	---	10622	BK, WH	---	(1) 18W (GU24)	10	9.5	5	5	Frosted Ribbed Glass.
G	6052	---	AZ, WH	(2) 150W (M)	---	6	11.25	---	---	Fixture can be wall or ceiling mounted.
H	6051	---	AZ, WH	(1) 150W (M)	---	6	11.25	---	---	Fixture can be wall or ceiling mounted.
J	1148	---	BK, TZ, WH	(1) 75W (M)	---	4.5	7.5	5.75	2.5	(18-25W CFL) Clear Glass.

Measurements shown in inches. U.S. Patent Pending: C, D, E.

DARK SKY ACCESSORIES



9649 CV
Alameda™
Panel Set 4820 WH



9651 CV
Alameda™
Panel Set 4812 WH



9652 CV
Alameda™
Panel Set 4813 WH



9849 CV
Alameda™
Panel Set 4814 WH



4822 OZ
Dark Sky Adapter



4822 BK
Dark Sky Adapter



Evening View of Outdoor Lantern without Dark Sky Panel Inserts



Evening View of Outdoor Lantern with Dark Sky Panel Inserts

Help fight light pollution with Kichler® Dark Sky Accessories. Made of lightweight, powder coated aluminum, our Dark Sky panels easily slide behind your light fixture's existing glass. During the day, your light fixture may look conventional. Yet, at night, the panels prevent light from passing through its glass – only to emit a subtle downlight from the fixture's open bottom.

All Fixtures shown here can be retrofitted with a Dark Sky Adaptor Panel. Panel Sets consist of enough panels to retrofit one fixture. Installation instructions are included.

While we believe these panels will work for most current laws, Dark Sky and Turtle Protection legislation may have specific parameters that need to be met for a municipality or region. It is advisable to review the legislation to ensure compliance is met with these product additions.

Dark Sky
panel
insert sets

For use
with these
fixtures

4812 WH	9651 CV
4813 WH	9652 CV
4814 WH	9849 CV
4820 WH	9649 CV

4822 OZ, BK is compatible with one-light, medium base fixtures facing downward where the exterior fixture can accommodate the dark sky adaptor.





Xenon Address Light 43800 BKT



LED Address Light 43800 OZLED

ADDRESS LIGHT

TEXTURED BLACK OR OLDE BRONZE® FINISH



A | 43800 OZ
Xenon Address Light
ADA Compliant



A | 43800 BKT
Xenon Address Light
ADA Compliant



B | 43800 BKTLED
LED Address Light
ADA Compliant



B | 43800 OZLED
LED Address Light
ADA Compliant



C | 4301
#1 Block



D | 4302
#2 Block



E | 4303
#3 Block



F | 4304
#4 Block



G | 4305
#5 Block



H | 4306
#6 Block



J | 4307
#7 Block



K | 4308
#8 Block



L | 4309
#9 Block



M | 4300
#0 Block



N | 4310
Blank Block



O | 4311
2 Blank
Half Blocks



P | 4381
Transformer

Q | 4355 CLR

ADDRESS LIGHT

CAST ALUMINUM
CONSTRUCTION

ITEM #	LED ITEM #	FINISH	INCAND. BULB	LIGHT SOURCE	W	H	L	EXT.	HCWO	NOTES
A	43800	BKT, OZ	(2) 5W (WED5) Ⓢ	---	2.5	7	12.25	2.5	3.5	Ⓢ Ⓣ
B	---	BKT, OZ	---	4W Ⓢ	2.5	7	12.25	2.5	3.5	Ⓢ Ⓣ
C	4301	---	---	---	2.25	5	.25	---	---	
D	4302	---	---	---	2.25	5	.25	---	---	
E	4303	---	---	---	2.25	5	.25	---	---	
F	4304	---	---	---	2.25	5	.25	---	---	
G	4305	---	---	---	2.25	5	.25	---	---	
H	4306	---	---	---	2.25	5	.25	---	---	
J	4307	---	---	---	2.25	5	.25	---	---	
K	4308	---	---	---	2.25	5	.25	---	---	
L	4309	---	---	---	2.25	5	.25	---	---	
M	4300	---	---	---	2.25	5	.25	---	---	
N	4310	---	---	---	2.25	5	.25	---	---	
O	4311	---	---	---	2.25	5	.25	---	---	
P	4381	---	---	---	2.75	2.5	2	---	---	Optional: Necessary only when doorbell transformer unavailable for installation. 16V output.
Q	4355	CLR	(1) 5W (WED5)	---	0.5	1	---	---	---	

Measurements shown in inches.



ACCESSORIES

DECORATIVE LAMP POSTS & PEDESTAL MOUNTS



A | 9523 BKT, LD
Shown with Tournai™
Lantern 9565 LD



B | 9510 BK, LD, OZ



D | 9542 BK, BST, LD, OZ



C | 9506 AZ, BK, OZ, TZ, WZC



E | 9595 AGZ, BK, BST, OZ



AGZ
Aged Bronze



AZ
Architectural Bronze™



BA
Brushed Aluminum



BK
Black



BKT
Textured Black



BST
Brown Stone



LD
Londonderry™



OB
Olde Brick®



OZ
Olde Bronze®



PB
Polished Brass



RZ
Rubbed Bronze™



TZ
Tannery Bronze™



TZG
Tannery Bronze™
with Gold




WH
White


DECORATIVE LAMP POSTS

	ITEM #	FINISH	W	H	NOTES
A	9523	BKT, LD	4	96	Cast Aluminum Pedestal Mount, Hardware included (J-bolts).
B	9510	BK, LD, OZ	12.75	72	Cast Aluminum Post, hardware included (J-bolts) for use at time of concrete base pour.
C	9506	AZ, BK, OZ, TZ, WZC	3	84	Direct Burial Aluminum Post.
D	9542	BK, BST, LD, OZ	3	96	Cast Aluminum Post, hardware included (J-bolts) for use at time of concrete base pour.
E	9595	AGZ, BK, BST, OZ	3	84	Direct Burial Fluted Aluminum Post.

Measurements shown in inches.



F | 9501 BK, WH **G** | 9502 BK **H** | 9505 AZ **J** | 49904 AZ, BK, WH **K** | 49907 AZ, BK, WH



L | 49914 AZ, BK **M** | 49950 BK **N** | 49951 BK, WH **O** | 49952 BK, WH **P** | 49953 AZ, BK, WH



Q | 9531 BK **R** | 9540 BKT, LD **R** | 9540 BKT, LD **S** | 9530 BK, OB, OZ, PB, WH, WZC **T** | 9549 BKT **T** | 9549 LD



U | 9551 BK **V** | 9592 AGZ **V** | 9592 AZ **V** | 9592 BK **V** | 9592 RZ


LAMP POSTS, PEDESTAL MOUNT ADAPTERS & MISCELLANEOUS

ITEM #	FINISH	W	H	L	NOTES
F	9501 BK, WH	3	84	---	Direct Burial Aluminum Post with Ladder Rest.
G	9502 BK	3	84	---	Direct Burial Aluminum Post with Ladder Rest and Internal Photocell (Repl. Internal Photocell 49950).
H	9505 AZ	3	84	---	Direct Burial Aluminum Post with Ladder Rest.
J	49904 AZ, BK, WH	3	84	---	Direct Burial Aluminum Post with Ladder Rest and External Photocell (Repl. External Photocell 49951).
K	49907 AZ, BK, WH	3	84	---	Direct Burial Aluminum Post with Ladder Rest, External Photocell and GCO (Replacement External Photocell 49951 or GCO 49952).
L	49914 AZ, BK	3	144	---	Direct Burial Aluminum Post
M	49950 BK	---	---	---	Replacement Internal Photocell (Black Only) (Not Shown).
N	49951 BK, WH	---	---	---	Replacement External Photocell (Not Shown).
O	49952 BK, WH	---	---	---	Replacement GCO (Not Shown).
P	49953 AZ, BK, WH	---	1.5	15.75	Replacement Ladder Rest.
Q	9531 BK	8	9	---	Cast Aluminum Pedestal Mount, hardware included (#10 Philips, SS wood screws).
R	9540 BKT, LD	10	4.75	---	Cast Aluminum Pedestal Mount, hardware included (J-bolts).
S	9530 BK, OB, OZ, PB, WH, WZC	7	3.5	---	Cast Aluminum Pedestal Mount (PB is Solid Cast Brass), hardware not included.
T	9549 BKT, LD	10	5.75	---	Cast Aluminum Pedestal Mount, hardware included (J-bolts).
U	9551 BK	9.5	9.5	---	Cast Aluminum Pedestal Mount, hardware included (#10 Philips, SS wood screws).
V	9592 AGZ, AZ, BK, RZ	5.75	3.5	---	Cast Aluminum Pedestal Mount

Measurements shown in inches. Do not mount post to Pedestal Mount Adaptor. Fixtures assemble directly to Adaptor.

LIGHT BULB REFERENCE & ACCESSORIES

Incandescent and Compact Fluorescent Light Bulbs



Compact Fluorescent Bulbs (CFL)



Look for this symbol throughout our catalog. This symbol indicates the products best suited for Indoor use with self-ballasted, compact fluorescent lamps sold through electrical distributors and lighting showrooms across the U.S.



This symbol indicates the product best suited for Outdoor use with self-ballasted, compact fluorescent lamps sold through electrical distributors and lighting showrooms across the U.S.

If a light fixture is connected to a dimmer or 3-way switch, you'll need to use a qualified CFL designed to work in these applications. Make sure to look for CFLs that specify use with dimmers or 3-way switches.

Equivalent Light Output

To determine which qualified CFL light bulbs will provide the same amount of light as your current incandescent light bulbs, consult the following chart:

	INCANDESCENT LIGHT BULBS WATTS (W)	INCANDESCENT MINIMUM LIGHT OUTPUT LUMENS	COMMON CFL LIGHT BULBS WATTS (W)
	40	450	9-13
	60	800	13-15
	75	1,100	18-25
	100	1,600	23-30
	150	2,600	30-52

Light-Emitting Diode (LED)









Look for this symbol throughout our catalog. This symbol indicates fixtures with an integrated LED light source.

LED Light Fixtures and Dimmer Switches

Refer to our listing of recommended dimmer switches that can be used with our LED light fixtures at: kichler.com/dimming

Fluorescent Lamps

PRODUCT ID	DESCRIPTION	
4013	Replacement Ballast, PL 26	
4014	Replacement Lamp, PLC 26, G24q-3 Base	
4025	Replacement Lamp, PLC 13, G24q-1 Base	
4026	Replacement Lamp, PLC 18, G24q-2 Base	
4028	Replacement Lamp, 2C T6 40W, G10q Base	
4029	Replacement Lamp, 2C T6 55W, G10q Base	
4030	Replacement Lamp, 2C T6 70W, G10q Base	
4033	Replacement Lamp, 13 Watt Anti-Turn Ballast	
4035	Replacement Ballast, 55W circline, G10q Base	
4036	Replacement Ballast, 70W circline, G10q Base	

PRODUCT ID	DESCRIPTION	
4043	Replacement Lamp, MLS13GUWW, 13W, GU24	
4044	Replacement Lamp, MLS18GUWW, 18W, GU24	
4045	Replacement Lamp, MLS26GUWW, 26W, GU24	
4050	Replacement Lamp, 13 Watt GU24 Squat Bulb	
4051	Replacement Lamp, 18 Watt GU24 Squat Bulb	
4074	Replacement Lamp, 11 Watt GU24 Spiral Bulb	
4075	Replacement Lamp, 18 Watt GU24 Quad Tube Bulb	
4089	Replacement Lamp, T9 32W Circline Bulb	
4090	Replacement Lamp, T9 40W Circline Bulb	
4094	Replacement Lamp, 14W Fluorescent Bulb	

Halogen & Krypton Lamps

PRODUCT ID	DESCRIPTION
4355 CLR	Bulb wedge base 5W 12V Xenon
5901 CLR	Clear 50W T-3 Double Contact, Bayonet Base, Tungsten (Suitable for use with all Kichler lights requiring Halogen Lamps)
5902 FST	Frosted 50W GU10 Halogen Lamp
5903 CLR	Clear 100W T-3 Mini-Can Base, Tungsten Halogen Lamp
5904 CLR	Clear 20W T-3 Candelabra Base Krypton Lamp
5904 FST	Frosted 20W T-3 Candelabra Base Krypton Lamp

PRODUCT ID	DESCRIPTION
5905 CLR	Clear 60W T-3 Candelabra Base Krypton Lamp
5905 FST	Frosted 60W T-3 Candelabra Base Krypton Lamp
5907 CLR	Clear 40W T-3 Candelabra Base Krypton Lamp
5907 FST	Frosted 40W T-3 Candelabra Base Krypton Lamp
5908 FST	Frosted 60W G9 Halogen Lamp
5909	50W MR16 Shielded GU10 Lamp
5910 CLR	Clear 75W T-3 Mini-Can Base, Tungsten Halogen Lamp
5911 CLR	E11 75W Mini-can halogen bulb

Decorative Light Bulbs



4071 CLR
60W (M)



5971 CLR
40W (C)

Standard Gauge Chain

Chain may be ordered in 3' lengths to supplement existing chain supplied with Kichler® fixtures. To order additional chain, look for the chain recommendations listed for fixtures requiring chain.

Extra Heavy Gauge Chain

- 4908 BK Black
- 4908 LD Londonderry™
- 4909 ESP Espresso
- 4930 BK Black
- 4930 LD Londonderry™

Outdoor Solid Brass Chain

- 4927 ACO Antique Copper
- 4927 AGZ Aged Bronze
- 4927 AVI Anvil Iron
- 4927 AZ Architectural Bronze®
- 4927 BK Black
- 4927 BKG Black with Gold
- 4927 BRZ Brushed Bronze
- 4927 CV Canyon View™
- 4927 DCO Distressed Copper
- 4927 GNT Textured Granite
- 4927 LD Londonderry™

- 4927 OB Olde Brick®
- 4927 OZ Olde Bronze®
- 4927 PL Platinum
- 4927 PR Prairie Rock™
- 4927 RST Rustic™
- 4927 RZ Rubbed Bronze
- 4927 SS Stainless Steel
- 4927 TZ Tannery Bronze™
- 4927 WZC Weathered Zinc

INDEX












345 BK	183	9039 RZ	142	9492 OZ	146	9611 OZ	183
345 TZ	183	9039 BK	144	9501 BK	189	9611 OZS	183
365 BK	183	9040 RZ	142	9501 WH	189	9611 SS	183
365 TZ	183	9040 BK	144	9502 BK	189	9611 SSS	183
1148 BK	184	9041 RZ	142	9505 AZ	189	9611 TZ	183
1148 TZ	184	9041 BK	144	9506 AZ	188	9611 TZS	183
1148 WH	184	9042 RZ	142	9506 BK	188	9611 WH	183
2621 NI	82	9042 BK	144	9506 OZ	188	9618 OZ	183
2713 NI	82	9043 RZ	142	9506 TZ	188	9618 SS	183
2713 OB	82	9043 BK	144	9506 WZC	188	9631 OZ	166
4300	187	9044 NI	82	9510 BK	188	9649 CV	97
4301	187	9060 RZ	139	9510 LD	188	9650 BK	181
4302	187	9060 BKT	141	9510 OZ	188	9650 TZ	181
4303	187	9095 AZ	184	9511 PR	102	9650 WH	181
4304	187	9109 BA	40	9523 BKT	188	9651 CV	97
4305	187	9109 BK	40	9523 LD	188	9652 CV	97
4306	187	9128 AGZ	106	9529 AGZ	106	9653 BK	181
4307	187	9129 AGZ	106	9530 BK	189	9653 TZ	181
4308	187	9130 AGZ	106	9530 OB	189	9653 WH	181
4309	187	9142 BK	82	9530 OZ	189	9654 BK	181
4310	187	9142 NI	82	9530 PB	189	9654 TZ	181
4311	187	9142 OZ	82	9530 WH	189	9654 WH	181
4355 CLR	187	9148 CV	97	9530 WZC	189	9655 BK	181
4381	187	9166 AZ	66	9531 BK	189	9655 TZ	181
6040 AZ	40	9167 AZ	66	9532 RZ	139	9676 OZ	166
6040 NI	40	9168 AZ	66	9532 BKT	141	9677 OZ	166
6048 AZ	40	9234 AZ	38	9533 RZ	139	9703 OZ	133
6048 NI	40	9234 BA	38	9533 BKT	141	9704 OZ	132
6051 AZ	184	9234 WH	38	9538 RZ	139	9704 BK	134
6051 WH	184	9236 AZ	38	9538 BKT	141	9707 BK	134
6052 AZ	184	9244 AZ	38	9539 RZ	139	9707 OZ	132
6052 WH	184	9244 BA	38	9539 BKT	141	9707 OZLED	32
9021 BK	82	9244 WH	38	9540 BKT	189	9708 BK	134
9021 NI	82	9246 AZ	38	9540 LD	189	9708 OZ	132
9021 OZ	82	9246 BA	38	9542 BK	188	9708 OZLED	32
9022 BK	82	9246 WH	38	9542 BST	188	9709 BK	134
9022 NI	82	9320 BK	183	9542 LD	188	9709 OZ	132
9022 OB	82	9320 WH	183	9542 OZ	188	9709 OZLED	32
9022 OZ	82	9322 WH	172	9549 BKT	189	9711 PB	149
9022 WH	82	9322 BK	183	9549 LD	189	9712 PB	149
9023 BK	82	9322 WH	183	9551 BK	189	9713 PB	149
9023 NI	82	9347 OZ	167	9557 AZ	63	9718 PR	102
9023 OB	82	9348 OZ	167	9558 LD	128	9719 PR	102
9023 OZ	82	9355 LD	126	9558 BKT	131	9720 PR	102
9024 DCO	108	9355 BKT	130	9559 LD	128	9721 PR	102
9025 DCO	108	9356 LD	126	9559 BKT	131	9735 BK	178
9027 DCO	108	9356 BKT	130	9564 LD	128	9735 TZ	178
9028 TZ	174	9357 LD	126	9564 BKT	131	9736 BK	178
9028 BK	175	9357 BKT	130	9565 LD	128	9736 TZ	178
9029 TZ	174	9358 LD	127	9565 BKT	131	9759 RST	79
9029 BK	175	9358 BKT	130	9568 LD	128	9760 RST	78
9030 TZ	174	9359 LD	127	9568 BKT	131	9761 RST	78
9030 BK	175	9359 BKT	130	9592 AGZ	189	9762 RST	78
9031 DCO	108	9360 LD	127	9592 AZ	189	9774 BK	170
9032 RZ	138	9360 BKT	130	9592 BK	189	9774 BKS	171
9032 BKT	140	9362** LD	125	9592 RZ	189	9774 WH	172
9033 RZ	138	9362** BKT	129	9595 AGZ	188	9776 BK	170
9033 BKT	140	9409 PB	148	9595 BK	188	9776 BKS	171
9034 RZ	138	9412 OZ	146	9595 BST	188	9776 WH	172
9034 BKT	140	9439 PB	148	9595 OZ	188	9777 BK	170
9035 RZ	138	9452 OZ	146	9611 BK	183	9777 WH	172
9035 BKT	140	9489 PB	148	9611 BKS	183	9783 OZ	173

9784 OZ	173	9920 DCO	108	43800 OZLED	187	49160 OZFL	104
9785 OZ	173	9931 OZ	166	49006 AVI	77	49161 OZ	104
9788 BK	177	9932 OZ	147	49007 AVI	77	49162 OZ	104
9788 TZ	177	9935 BK	179	49059 OZ	83	49164 OZ	104
9789 BK	177	9935 TZ	179	49060 OZ	83	49183 BK	178
9789 TZ	177	9938 RZ	143	49061 OZ	83	49183 TZ	178
9790 BK	177	9938 BK	145	49062 OZ	83	49185 BK	177
9790 TZ	177	9940 RZ	143	49063 OZ	83	49185 TZ	177
9791 BK	177	9940 BK	145	49064 OZ	75	49186 BK	178
9791 TZ	177	9953 CV	99	49065 OZ	76	49186 TZ	178
9794 BK	178	9956 BK	181	49065 OZLED	33	49187 BK	179
9794 TZ	178	9956 TZ	181	49067 OZ	76	49187 TZ	179
9804 OZ	133	9962 RST	79	49067 OZLED	33	49190 AZLED	25
9804 BK	135	9967 AZ	66	49071 BST	67	49200 BK	58
9805 BK	181	9985 OZ	173	49071 BSTFL	67	49200 BKFL	58
9805 TZ	181	9989 PB	148	49072 BST	67	49201 BK	58
9805 WH	181	9992 BK	177	49072 BSTFL	67	49201 BKFL	58
9809 BK	135	9992 TZ	177	49073 BST	67	49202 BK	58
9809 OZ	133	10622 BK	184	49073 BSTFL	67	49202 BKFL	58
9809 OZLED	32	10622 WH	184	49074 BST	67	49203 BK	58
9810 TZ	174	10640 AZ	40	49074 BSTFL	67	49203 BKFL	58
9810 BK	175	10640 NI	40	49075 BST	67	49205 BK	58
9811 PR	102	10907 OZ	136	49075 BSTFL	67	49205 BKFL	58
9817 AP	183	10908 OZ	136	49091 CV	45, 99	49206 BK	58
9825 CV	99	10909 OZ	136	49110 AVI	184	49206 BKFL	58
9830 AGZ	106	10911 OZ	136	49117 AZLED	25	49207 BK	58
9831 OZ	166	10922 AZ	184	49118 AZLED	25	49207 BKFL	58
9832 OZ	147	10923 BK	184	49119 AVI	56	49226 OZ	61
9834 WH	38	10923 TZ	184	49119 AVIFL	56	49226 OZLED	35
9835 BK	179	10941 BK	184	49120 AVI	56	49227 OZ	61
9835 TZ	179	10950 TZ	180	49120 AVIFL	56	49227 OZLED	35
9837 DCO	108	10953 TZ	180	49121 AVI	56	49228 OZ	61
9838 DCO	108	10954 TZ	180	49121 AVIFL	56	49228 OZLED	35
9843 RZ	143	10956 TZ	180	49122 AVI	56	49229 OZ	61
9843 BK	145	11001 RZ	142	49122 AVIFL	56	49229 OZLED	35
9848 RZ	143	11002 RZ	142	49123 AVI	56	49232 OZ	61
9848 BK	145	11010 RZ	137	49124 AVI	56	49248 AGZLED	34
9849 CV	99	11011 RZ	137	49125 AVI	56	49249 AGZLED	34
9850 BK	181	11012 RZ	137	49130 BRZ	160	49252 AZTLED	33
9850 TZ	181	11013 RZ	137	49130 BKG	162	49253 AZTLED	33
9854 LD	128	11014 RZ	137	49131 BRZ	160	49255 BK	170
9854 BKT	131	11016 RZ	137	49131 BKG	162	49255 TZ	170
9855 LD	128	11017 PR	102	49132 BRZ	160	49255 BKS	171
9855 BKT	131	11018 PR	102	49132 BKG	162	49255 WH	172
9859 TZ	174, 183	11019 PR	102	49133 BRZ	160	49256 BK	170
9859 BK	175, 183	11020 PR	102	49133 BKG	162	49256 TZ	170
9870 RST	79	11028 BK	183	49134 BRZ	160	49256 BKS	171
9885 OZ	173	11028 WH	183	49134 BKG	162	49256 WH	172
9886 BKS	168, 171	11067 AZFL	66	49135 BRZ	160	49257 AZ	95
9886 OZS	169	11068 AZFL	66	49135 BKG	162	49257 AZFL	95
9886 BK	170, 177, 179	11069 AZFL	66	49136 BRZ	160	49258 AZ	95
9886 TZ	170, 177, 179	11077 AZT30	37	49136 BKG	162	49258 AZFL	95
9889 PB	148	11077 BKT30	37	49149 AZ	41	49263 BA	76
9892 BK	177	11098 NI	82	49151 AZ	41	49270 RZ	65
9892 TZ	177	11099 NI	82	49153 AGZVM	100	49271 RZ	65
9902 PR	102	11250 AZT30	37	49157 OZ	104	49272 RZ	65
9909 BK	135	11250 BKT30	37	49157 OZFL	104	49273 RZ	65
9909 OZ	133	11251 AZT30	37	49158 OZ	104	49274 RZ	65
9909 OZLED	32	11251 BKT30	37	49158 OZFL	104	49277 WZC	158
9913 PB	149	43800 BKT	187	49159 OZ	104	49278 AZTLED	19
9918 TZ	174	43800 BKTLED	187	49159 OZFL	104	49278 PLLED	19
9918 BK	175	43800 OZ	187	49160 OZ	104	49279 AZTLED	19

INDEX

49279 PLED.....	19	49475 RZFL.....	54	49588 OZ.....	45, 81	49674 OZ.....	89
49291 OZ.....	120	49476 RZ.....	54	49590 OZ.....	44	49675 OZ.....	89
49292 OZ.....	120	49476 RZFL.....	54	49600 LD.....	111	49676 OZ.....	89
49293 OZ.....	120	49478 RZ.....	54	49601 LD.....	111	49677 OZ.....	89
49294 OZ.....	121	49492 AZ.....	31	49602 LD.....	111	49678 OZ.....	89
49295 OZ.....	121	49492 PL.....	31	49603 LD.....	45, 111	49681 OZ.....	87
49336 AZ.....	68	49492 SBK.....	31	49604 LD.....	111	49682 OZ.....	87
49337 AZ.....	68	49493 RZ.....	54	49605 OZLED.....	20	49683 OZ.....	87
49338 AZ.....	68	49494 AZ.....	29	49606 OZLED.....	20	49684 OZ.....	87
49339 AZ.....	68	49494 PL.....	29	49607 AZTLED.....	21	49685 OZ.....	87
49341 AZ.....	69	49494 SBK.....	29	49608 AZTLED.....	21	49691 BKT.....	73
49342 AZ.....	69	49496 AZ.....	50	49611 OZ.....	122	49692 BKT.....	73
49343 AZ.....	69	49496 BA.....	52	49612 OZ.....	122	49693 BKT.....	73
49344 AZ.....	62	49497 AZ.....	50	49613 OZ.....	122	49694 BKT.....	73
49344 AZFL.....	62	49497 BA.....	52	49614 OZ.....	122	49695 BKT.....	73
49344 PSS316.....	64	49498 AZ.....	44, 49	49615 OZ.....	122	49696 BKT.....	44, 73
49345 AZ.....	62	49499 RZ.....	54	49616 OZ.....	122	49700 WZC.....	114
49345 AZFL.....	62	49501 OZ.....	156	49617 OZ.....	122	49701 WZC.....	114
49345 PSS316.....	64	49501 WZC.....	158	49618 OZ.....	107	49702 WZC.....	114
49346 AZ.....	62	49502 OZ.....	155	49619 OZ.....	107	49703 WZC.....	114
49346 AZFL.....	62	49502 WZC.....	158	49620 OZ.....	107	49704 WZC.....	115
49346 PSS316.....	64	49503 OZ.....	156	49621 OZ.....	107	49705 WZC.....	115
49348 AZ.....	63	49503 WZC.....	158	49622 BKTLED.....	26	49709 OZ.....	117
49349 AZ.....	63	49504 OZ.....	156	49623 BKTLED.....	26	49710 OZ.....	117
49349 PSS316.....	64	49504 WZC.....	158	49624 BKTLED.....	26	49711 OZ.....	117
49381 OZ.....	110	49505 OZ.....	156	49625 BKTLED.....	26	49712 OZ.....	117
49382 OZ.....	110	49505 WZC.....	158	49626 BKTLED.....	26	49713 OZ.....	117
49383 OZ.....	110	49506 OZ.....	156	49627 WZC.....	85	49714 OZ.....	113
49384 OZ.....	151	49506 WZC.....	158	49628 WZC.....	85	49715 OZ.....	113
49385 OZ.....	152	49519 AZTLED.....	27	49629 WZC.....	85	49716 OZ.....	113
49386 OZ.....	152	49519 BKTLED.....	27	49630 WZC.....	85	49717 OZ.....	113
49387 OZ.....	153	49520 AZTLED.....	27	49631 WZC.....	85	49718 OZ.....	113
49388 OZ.....	153	49521 AZTLED.....	27	49632 WZC.....	85	49904 AZ.....	189
49389 OZ.....	153	49538 BALED.....	22	49638 OZ.....	45, 92	49904 BK.....	189
49394 OZ.....	110	49538 OZLED.....	22	49640 OZ.....	92	49904 WH.....	189
49434 AZ.....	31	49539 BALED.....	23	49641 OZ.....	92	49907 AZ.....	189
49434 PL.....	31	49539 OZLED.....	23	49642 OZ.....	92	49907 BK.....	189
49434 SBK.....	31	49550 AZLED.....	36	49642 OZFL.....	92	49907 WH.....	189
49435 AZ.....	31	49550 BKTLED.....	36	49643 OZ.....	92	49914 AZ.....	189
49435 PL.....	31	49551 AZLED.....	36	49643 OZFL.....	92	49914 BK.....	189
49435 SBK.....	31	49551 BKTLED.....	36	49644 OZ.....	92	49950 BK.....	189
49436 AZ.....	29	49552 BKT.....	165	49644 OZFL.....	92	49951 BK.....	189
49436 PL.....	29	49553 BKT.....	165	49646 OZ.....	92	49951 WH.....	189
49436 SBK.....	29	49554 BKT.....	165	49654 BK.....	168	49952 BK.....	189
49437 AZ.....	29	49555 BKT.....	165	49654 OZ.....	169	49952 WH.....	189
49437 PL.....	29	49556 BKT.....	165	49655 BK.....	168	49953 AZ.....	189
49437 SBK.....	29	49557 AZLED.....	18	49655 OZ.....	169	49953 BK.....	189
49444 AZ.....	50	49558 AZLED.....	18	49656 BK.....	168	49953 WH.....	189
49444 BA.....	52	49569 WZC.....	70	49656 OZ.....	169	310131 NI.....	82
49445 AZ.....	50	49570 WZC.....	70	49657 BK.....	168	310131 OZ.....	82
49445 BA.....	52	49571 WZC.....	70	49657 OZ.....	169		
49446 AZ.....	50	49572 WZC.....	70	49658 BK.....	168		
49446 BA.....	52	49573 WZC.....	70	49658 OZ.....	169		
49447 AZ.....	50	49577 BKTP.....	184	49660 WZC.....	90		
49447 BA.....	52	49579 OZ.....	118	49661 WZC.....	90		
49449 AGZ.....	100	49580 OZ.....	118	49662 WZC.....	90		
49450 AGZ.....	100	49581 OZ.....	118	49663 WZC.....	91		
49451 AGZ.....	100	49582 OZ.....	119	49664 WZC.....	91		
49452 AGZ.....	100	49583 OZ.....	119	49667 WZC.....	44, 70		
49453 AGZ.....	100	49585 OZ.....	81	49668 WZC.....	70		
49474 RZ.....	54	49586 OZ.....	81	49669 WZC.....	70		
49475 RZ.....	54	49587 OZ.....	81	49671 AZ.....	44		

LEGEND/SYMBOL GUIDE

-  = This symbol indicates the product best suited for Indoor use with self-ballasted, compact fluorescent lamps sold through electrical distributors and lighting showrooms across the U.S.
-  = This symbol indicates the product best suited for Outdoor use with self-ballasted, compact fluorescent lamps sold through electrical distributors and lighting showrooms across the U.S.
- (C) = Candelabra base lamp (E-12).
- (C/K) = Candelabra base lamp (E-12) or Krypton candelabra base lamp.
- (K) = Krypton candelabra base lamp.
- (M) = Medium base lamp (E-26).
- (MNCN) = Mini-can base halogen lamp
- ✓ = Fixture requires supply wire rated for at least 75° C
- ❖ = Fixture requires supply wire rated for at least 90° C
- ☆ = When electrical connection is made inside the fixture, supply wire must be rated at least 75° C. When electrical connection is made in an outlet box, supply wire must be rated at least 60° C.
- ① = Installation Instructions: Fixture must be supported independently of the outlet box unless the outlet box is UL listed for the weight to be supported. Consult a qualified electrician/installer. Required installation parts included.
- D = Diameter
- Ext. = Extension
- Fluor. = Fluorescent
- H = Height
- HCWO = Height from Center of Wall Opening
- Incand. = Incandescent
- L = Length
- Ovrll. H = Overall Height
- W = Width
- Extra Wire = Extra wire beyond chain and/or stems
- Chain/Stem = Length of chain or stem supplied with fixture
-  = Title 24 is a document that contains the building codes for the state of California. All lighting fixtures in this catalog that comply with the Aug. 1, 2009 revision of the California Title 24 standards are marked with the T24 logo. For more information, visit www.energy.ca.gov/title24
-  = UL DAMP
-  = UL WET
-  = Dark Sky Compliant
-  = ADA Compliant (American Disabilities Act)
-  = LED (Light Emitting Diode)
-  = Energy Star
-  = FCC Federal Communications Commission. Devices with this logo comply with part 15 of the FCC rules.
-  = Lamp Included
- * = Kichler® Products are not produced or associated with any Native American Indians, nor are they a Native American product or the product of a particular Indian, Indian tribe or Indian arts and crafts organization as defined by 25 U.S.C. §305 et. seq.

- Bulbs not included unless otherwise noted.
- Wattages stated are the maximum recommended, however, you may use lower wattage lamps to suit your lighting needs. Some recommended lamps are not available in the maximum allowable wattage.
- All electrical products are rated as 120-volt, AC unless otherwise noted.
- All electrical products are certified and listed to UL/CSA/ETL Standards for use in U.S.A. and Canada except where noted.
- All products featured in the outdoor section are certified and listed to UL/CSA/ETL standards for wet location except where noted.
- Finishes for fixtures installed outdoors are subject to change due to prolonged exposure to sunlight, airborne pollutants and other forms of weathering.
- Many long life tungsten halogen capsule lamps are now available as alternates to conventional incandescent light bulbs. The halogen capsule lamps may be used to replace any lamp of a higher wattage, but not to exceed the existing specified maximum wattage, i.e., 72W may replace a 75W.
- On some products, in order to accommodate higher than normal ceiling height, extra lead wire is supplied and specified. With additional sections of chain or stems (not included), this allows an added measure of design flexibility.
- All chain drop products equipped with at least 72" of chain unless otherwise noted.
- To serve you better, Kichler® reserves the right to make improvements to the products in this catalog. Therefore, some products may change during the life of the catalog and the product information contained in this catalog may also have changed.

Consumer Notice

Federal Legislation to phase out 100 watt Incandescent Bulbs started January 2012

The federal government enacted the Energy Independence and Security Act of 2007 in December 2007, requiring all general-purpose light bulbs that produce 310–2600 lumens of light be 30% more energy efficient (similar to current halogen lamps) than current incandescent bulbs by 2014. The efficiency standards started with 100 watt bulbs in January 2012 and will end with 40 watt bulbs in January 2014.

Light bulbs outside of this range are exempt from the restrictions (historically, less than 40 watts or more than 150 watts). Also exempt are several classes of specialty lights, including appliance lamps, rough service bulbs, 3-way, colored lamps, and plant lights.

By 2020, a second tier of restrictions would become effective; which requires all general-purpose bulbs to produce at least 45 lumens per watt (similar to current CFLs). Exempt from the Act are reflector flood, 3-way, candelabra, colored, and other specialty bulbs.

Many Governments worldwide have passed measures to prohibit the sale of incandescent light bulbs for general lighting. The aim is to encourage use of more energy efficient lighting alternatives, such as compact fluorescent lamps (CFLs) and LED lamps.

References: www.energy.senate.gov

We go to great lengths to assure the metal and glass finishes shown in the catalog match the actual products, but printing variations and variations in chemical finishes and the nature of hand applied finishing will cause some differences between the printed images and actual product, and from one product to another.

We use only non-ferrous materials on the exterior parts of our outdoor lantern products, and use the best available weather-resistant finishes. However, due to some extreme environmental conditions such as acid rain, salt air and ultraviolet exposure, we cannot guarantee our exterior finishes, with the exception of our LifeBrite® lanterns.

Due to environmental conditions such as soil acidity, concrete alkalinity and other corrosive soil and air conditions, we cannot guarantee our direct burial posts.

CONNECT WITH US



Become a fan of Kichler Lighting at: facebook.com, search Kichler Lighting



Follow us on twitter at: twitter.com/kichlerlight



Find us on Pinterest at: <http://pinterest.com/kichlerstyle/>



Join us on Houzz at: <http://www.houzz.com/pro/kichlerlighting/kichler>



Watch us on youtube.com/KichlerLighting

To find an Authorized Dealer, visit: www.kichler.com

KICHLER

World Headquarters
7711 E. Pleasant Valley Rd.
PO Box 318010
Cleveland, Ohio 44131-8010





Featured on Front Cover:
Harbor Row Collection
Outdoor Wall 49715 OZ, page 112

Featured on Back Cover:
Dahlia Collection
Outdoor Wall 49588 AZ, page 18

KICHLER

GET INSPIRED AT
KICHLER.COM
For more information call
866.558.5706

Catalog No. **K816**
www.kichler.com
Printed in USA
15-KD-3792-50M
© The L.D. Kichler Co.
All right reserved.