

CUSTOM easier & faster than you think

You pick a product... We customize In-House!

PAINTING




Boxes - Covers - Fittings
J-Hooks - Hangers/Supports

CUTTING




Conduit - Threaded Rod
Hangers - Supports - Strut

ELBOWS / NIPPLES



Any Length - Any Size
EMT or Rigid

BOXES / COVERS



We Can Modify Any Box to Meet
Your Job Requirements


NEW INVENTIONS

GOT A
PRODUCT
IDEA?



We Can Build It!

STAINLESS



Custom Boxes - Hubs - Bridle
Rings - J-Hooks - Beam Clamps

GARVIN
ELECTRICAL MANUFACTURER

847-455-0188
garvinindustries.com

PRODUCT Spotlight

WEATHERPROOF LED TEMPLIGHTS

Theft Proof LED Lamp

- IP64 Rated
- 5 Yr / 50,000 Hrs
- UL Listed




Pages 4-5

OIL TIGHT K.O. SEALS

Best Price Guaranteed

- 1/2" to 4" In Stock
- Galvanized or Stainless Steel




Page 191

ADJUSTABLE DEPTH RINGS

Extends to Finished Wall Depth

- One Gang to Four Gang
- Available: 4" Square, 4-11/16" Square, 5" Square, 6" Square, Octagon



Pages 198-237

SNAP-IN EMT FITTINGS

Quickest Connections

- Connectors & Couplings
- 1/2" to 4" In Stock
- UL Listed



Page 240

MAGNETIC CABLE SUPPORTS

Instant Wire Installs

- J-Hooks, Bridle Rings, & Cable Tie Mounts
- Pull Strength: Up to 90 Lbs



Pages 30, 33, 35

SLIP COUPLINGS

Slip On... Slide Over!

- 1/2" to 4" In Stock
- Compression or Set Screw

Pages 241, 244



PRODUCT Spotlight

MINI STEEL TEMPLIGHTS

Rugged Steel Lasts A Lifetime

- Versatile & Convenient
- Great for Small Spaces




Page 10

SCREW-ON CABLE SUPPORTS

Great for Tight Spaces

- 1/2" to 1-1/2" Loop




Page 40

CONCRETE SLAB BOX ASSEMBLIES

Stop Taping... Start Saving!

- Finished Assembly with Connectors & Covers
- Leak Proof Design



Page 106

WALL SCONCE TEMPLIGHT

Fits Any Box or Ring

- Adapter Plates Fits Any Box
- Rugged Steel Construction



Page 2

UNIVERSAL BREAKER LOCKS

Fits Any Manufacturer's Breaker

- 1 Pole, 2 Pole, & 3 Pole Models




Pages 287-289

48" T-GRID BRACKET

Fits 4 ft. Ceiling Tiles

- Adjustable Depth & Positioning
- Easy "Snap-On" Design



Page 77

PRODUCT Spotlight

OCTAGON LED TEMPLIGHT COVER

Stop Sagging Sockets

- 9 Watt LED Lamp
- Theft Proof Cage
- 5 Year Guarantee




Page 2

HINGED PREFAB BOXES

Instant Access Inside Box

- 1/2" & 3/4" K.O.'s
- Complete with Any Device Ring or Cover
- Also Available with Mounting Bracket




Pages 138-143

SQUARE TO OCTAGON RINGS

Extra Space for Drivers & Wires

- 5/8" Raised
- Raised 4" Octagon Opening



Page 204

LARGE DATA BOXES

Accepts Any Conduit & Innerduct

- 1/2" to 2" Concentric K.O.'s
- 3-1/4" Deep
- Multiple Grounding Provisions




Pages 133

MASONRY BOX EXTENSION RINGS

Fast Fit to Finished Surface


- 2-1/2" & 3-1/2" Deep
- 1 Gang to 9 Gang Available



CEILING TILE BRIDGES

Stops Sagging Devices

- 4" Square Mounting
- Slides to Any Position



Page 78

PRODUCT Spotlight

SELF CUTTING CABLE TIES

Zip...Twist...Done!

- No Tools
- No Sharp Edges
- FREE Samples



Page 28

LIGHT POLLUTION SHIELD

**Blocks Light...
Keeps Neighbors
Happy!**

- Opaque Surface Blocks Light Pollution
- Mirror Finish Interior



Page 12

WIDE MOUTH BEAM CLAMPS

Fits Any Flange Size!

- 3-1/2" Wide Jaw
- Rugged Iron Body



Page 81

CAN LIGHT BLANK UP COVERS

**Safely Cover
Recessed Cans**

- Multiple Sizes for Any Can Light Opening



Page 24

PREFAB BRACKET BOX CONNECTORS

Installs in Seconds

- For 1/2" K.O.'s
- Works with Caddy® & B-Line Fixed Position Brackets



Page 250

FLAT FLOOR CONDUIT PLUGS

**Protects Pipes...
Eliminates Stub Ups!**

- Fits 1/2", 3/4" & 1" EMT
- Eliminates Trip Hazard on Job Site



Page 252

LED & CFL LAMPS/BULBS

WEATHERPROOF LED LAMPS

- IP64 Rated for water splash, spray & dust ingress
- Input Voltage: 100-300
- Color Temp: 6500K
- Rated Life: 50,000 Hrs.
- Std. Pkg: 1



ITEM	WATTS	BASE	LUMENS	OVERALL LENGTH	PRICE EACH
LED40	40	Medium	4,500	10.25"	\$49.99
LED60	60	Medium	6,500	10.43"	\$59.99
LED80	80	Mogul	8,500	10.62"	\$79.99
LED100	100	Mogul	10,000	11.25"	\$99.99
LED120	120	Mogul	12,000	12.00"	\$119.99
LED150	150	Mogul	15,000	13.00"	\$149.99



• 360° ILLUMINATION



Bottom LEDs

105W COMPACT FLUORESCENT LAMPS

- Color Temp: 6500K
- Rated Life: 8,000 Hrs.
- Std. Pkg: 1



ITEM	BASE	VOLTAGE	LUMENS	OVERALL LENGTH	PRICE EACH
C105651MED	Medium	120	6,400	12.8"	\$24.99
C105652MOG	Mogul	277	12.8"	\$25.99	



LIGHTING

BOX-MOUNT TEMPLIGHT FIXTURES

UNIVERSAL WALL SCONCE TEMPLIGHT FIXTURE

- Interchangeable mounting plates fit any box or ring in wall
- Cage height: 5-7/8"
- Cage diameter: 4"
- Std. Pkg: 1



Item: TLMU

\$29.99 Each

ONE FIXTURE... FITS ALL



4" Octagon



3-1/2" Oct/Round



Square-to-Round



One-gang Rings



Switch Boxes



Handy Boxes


LED THEFT-RESISTANT TEMPLIGHT

- Fits 4" octagon & square-to-round rings
- Vandal-resistant steel cage protects LED lamp from theft
- Std. Pkg: 1




ITEM	WATTS	LUMENS	STD. PKG.	PRICE EACH
TLCO	9	1000	1	\$14.99

LED LINEAR HIGHBAY FIXTURES




BEFORE

ITEM	WATTS	LUMENS	L X W X D (INCHES)	COLOR TEMP.	STD. PKG.	PRICE EACH
LHB-804	80	11,121	23.8 x 12.6 x 3.62	4,000 K	1	\$179.00
LHB-805	80	11,121		5,000 K	1	\$179.00
LHB-1104	110	15,792		4,000 K	1	\$189.00
LHB-1105	110	16,406		5,000 K	1	\$189.00
LHB-1654	165	24,124		4,000 K	1	\$249.00
LHB-1655	165	24,563		5,000 K	1	\$249.00
LHB-2254	225	32,000	45.9 x 12.6 x 3.62	4,000 K	1	\$299.00
LHB-2255	225	32,000		5,000 K	1	\$299.00
LHB-3254	325	47,000	45.9 x 17.3 x 3.62	4,000 K	1	\$359.00
LHB-3255	325	47,000		5,000 K	1	\$359.00




AFTER

LED WALL PACK FIXTURES



BEFORE

ITEM	WATTS	LUMENS	SIZE	COLOR TEMP.	STD. PKG.	PRICE EACH
LWP-305	30	3,400	Medium	5,000 K	1	\$179.00
LWP-455	45	5,200			1	\$189.00
LWP-705	70	8,000			1	\$199.00
LWP-905	90	10,500	Large		1	\$299.00
LWP-1355	135	16,000			1	\$399.00



AFTER

LED WORK LIGHTS

MULTIPURPOSE LED WORK LIGHT

- Super-Bright Premium LEDs
- Complete with hook, magnet, tripod adapter & paint shield!
- Weatherproof & Shatter-Free lamp



HANG IT...HOOK



STICK IT...MAGNETS



RAISE IT...TRIPOD ADAPTER



SET IT...FLAT SURFACES

ITEM	WATTS	LUMENS	AC INPUT VOLTAGE	MAGNET STRENGTH	FITS TRIPODS	CORD	STD. PKG.	PRICE EACH
TLU-60	60	6,500	100-300	150 Lbs.	1/4-20 & 5/8-11	10 Ft.	1	\$120.00
TLU-100	100	10,000					1	\$180.00

THEFT-RESISTANT WEATHERPROOF LED TEMPLIGHTS WITH 10 FT. POWER CORD

- IP64 Rated for water spray & dust ingress
- Self-enclosed theft-proof lamp
- Std. Pkg: 1



ITEM	WATTS	LUMENS	INPUT VOLTAGE	OVERALL HEIGHT	PRICE EACH
TL60WP	60	6,500	100-300	13-1/2"	\$120.00
TL100WP	100	10,000			\$180.00

LED TEMPLIGHTS

- IP64 Rated for water spray & dust ingress
- Color Temp: 6500K
- Lamp Life: 50,000 Hrs.
- Cage Diameter: 6-3/4"
- Std. Pkg: 1



ITEM	WATTS	BASE	LUMENS	INPUT VOLTAGE	CAGE HEIGHT	PRICE EACH
TL40LED	40	Medium	4,500	100-300	13"	\$89.00
TL60LED	60	Medium	6,500		13"	\$99.99
TL80LED	80	Mogul	8,500		15-1/4"	\$149.99
TL100LED	100	Mogul	10,000		15-1/4"	\$159.99
TL120LED	120	Mogul	12,000		15-1/4"	\$169.99
TL150LED	150	Mogul	15,000		15-1/4"	\$199.99

LED TEMPLIGHTS WITH 6 FT. POWER CORD

- IP64 Rated for water spray & dust ingress
- Color Temp: 6500K
- Lamp Life: 50,000 Hrs.
- Cage Diameter: 6-3/4"
- Std. Pkg: 1



ITEM	WATTS	BASE	LUMENS	INPUT VOLTAGE	CAGE HEIGHT	PRICE EACH
TL40LEDW	40	Medium	4,500	100-300	13"	\$89.00
TL60LEDW	60	Medium	6,500		13"	\$109.99
TL80LEDW	80	Mogul	8,500		15-1/4"	\$159.99
TL100LEDW	100	Mogul	10,000		15-1/4"	\$169.99
TL120LEDW	120	Mogul	12,000		15-1/4"	\$179.99
TL150LEDW	150	Mogul	15,000		15-1/4"	\$209.99

LED TEMPLIGHTS WITH 6 FT. CORD & STRIPPED LEADS

- IP64 Rated for water spray & dust ingress
- Color Temp: 6500K
- Lamp Life: 50,000 Hrs.
- Cage Diameter: 6-3/4"
- Std. Pkg: 1



ITEM	WATTS	BASE	LUMENS	INPUT VOLTAGE	CAGE HEIGHT	PRICE EACH
TL40LEDWS	40	Medium	4,500	100-300	13"	\$94.99
TL60LEDWS	60	Medium	6,500		13"	\$109.99
TL80LEDWS	80	Mogul	8,500		15-1/4"	\$159.99
TL100LEDWS	100	Mogul	10,000		15-1/4"	\$169.99
TL120LEDWS	120	Mogul	12,000		15-1/4"	\$179.99
TL150LEDWS	150	Mogul	15,000		15-1/4"	\$209.99

LED & CFL TEMLIGHTS

LED TEMPLIGHT STRINGERS

- IP64 Rated for water spray & dust ingress
- Input voltage: 100-300
- Color Temp: 6500K
- Lamp Life: 50,000 Hrs.
- Cage Diameter: 6-3/4"
- Std. Pkg: 1



ITEM	WATTS	BASE	LUMENS	CAGE HEIGHT	PRICE EACH
TL40LEDPT	40	Medium	4,500	13"	\$99.99
TL60LEDPT	60	Medium	6,500	13"	\$119.99
TL80LEDPT	80	Mogul	8,500	15-1/4"	\$169.99
TL100LEDPT	100	Mogul	10,000	15-1/4"	\$179.99
TL120LEDPT	120	Mogul	12,000	15-1/4"	\$189.99
TL150LEDPT	150	Mogul	15,000	15-1/4"	\$219.99

105W COMPACT FLUORESCENT TEMLIGHTS

- Color Temp: 6500K
- Lamp Life: 8,000 Hrs.
- Cage Diameter: 6-3/4"
- Std. Pkg: 1



ITEM	BASE	LUMENS	INPUT VOLTAGE	CAGE HEIGHT	PRICE EACH
TL105CF	Medium	6,400	120	13"	\$59.99
TL105CF277	Mogul	6,400	277	13"	\$89.99





- Also works with LED lamps

105W COMPACT FLUORESCENT TEMLIGHTS WITH 6 FT. POWER CORD

- Color Temp: 6500K
- Lamp Life: 8,000 Hrs.
- Cage Diameter: 6-3/4"
- Std. Pkg: 1



ITEM	BASE	LUMENS	INPUT VOLTAGE	CAGE HEIGHT	PRICE EACH
TL105CFW	Medium	6,400	120	13"	\$69.99
TL105CF277W	Mogul	6,400	277	13"	\$99.99



- Also works with LED lamps

CALL FOR VOLUME DISCOUNTS!

847-455-0188

105W COMPACT FLUORESCENT TEMPLIGHTS WITH 6 FT. CORD & STRIPPED LEADS

- Color Temp: 6500K
- Lamp Life: 8,000 Hrs.
- Cage Diameter: 6-3/4"
- Std. Pkg: 1



ITEM	BASE	LUMENS	INPUT VOLTAGE	CAGE HEIGHT	PRICE EACH
TL105CFWS	Medium	6,400	120	13"	\$69.99
TL105CF277WS	Mogul	6,400	277	13"	\$99.99



- Also works with LED lamps

105W COMPACT FLUORESCENT TEMPLIGHT STRINGER

- Lumens: 6,400
- Color Temp: 6500K
- Lamp Life: 8,000 Hrs.
- Cage Diameter: 6-3/4"
- Std. Pkg: 1



ITEM	BASE	INPUT VOLTAGE	OVERALL HEIGHT	CAGE HEIGHT	PRICE EACH
TL105CFPT	Medium	120	19"	13"	\$99.00

- Plug & Play... Instant Illumination!
- String together with extension cords!
- Also works with LED lamps

Lamp Replacement Guide

IF YOU ARE REPLACING...	Select LED	Select CFL
100W Metal Halide	40W	105W
150W Metal Halide	60W	105W
175W Metal Halide	80W	150W
250W Metal Halide	100W	150W
400W Metal Halide	120W	200W
70W High Pressure Sodium	40W	105W
100W High Pressure Sodium	60W	150W
150W High Pressure Sodium	100W	200W
250W High Pressure Sodium	120W	-----

STANDARD TEMPLIGHT FIXTURES

MEDIUM-BASE TEMPLIGHT FIXTURE

- Weight: 2 lbs.
- Std. Pkg: 1



ITEM	OVERALL HEIGHT	CAGE LENGTH	CAGE DIAMETER	PRICE EACH
TLF	19"	13"	6-3/4"	\$51.99



- Also works with LED lamps

MEDIUM-BASE TEMPLIGHT FIXTURE WITH 6 FT. CORD

- Weight: 3 lbs.
- Std. Pkg: 1



ITEM	OVERALL HEIGHT	CAGE HEIGHT	CAGE DIAMETER	PRICE EACH
TLFW	19"	13"	6-3/4"	\$61.99



MEDIUM-BASE TEMPLIGHT FIXTURE WITH 6 FT. CORD & STRIPPED LEADS

- Weight: 3 lbs.
- Std. Pkg: 1



ITEM	OVERALL HEIGHT	CAGE HEIGHT	CAGE DIAMETER	PRICE EACH
TLFWS	19"	13"	6-3/4"	\$61.99



MEDIUM-BASE MAGNETIC TEMPLIGHT FIXTURE WITH 6 FT. POWER CORD

- Magnet: 90 lbs.
- Weight: 4 lbs.
- Std. Pkg: 1



ITEM	OVERALL HEIGHT	CAGE HEIGHT	CAGE DIAMETER	PRICE EACH
TLFMAGW	19"	13"	6-3/4"	\$69.99

STANDARD TEMPLIGHT FIXTURES

MOGUL-BASE TEMPLIGHT FIXTURE – ONLY

- Weight: 3 lbs.
- Std. Pkg: 1



ITEM	OVERALL HEIGHT	CAGE HEIGHT	CAGE DIAMETER	PRICE EACH
TLF-L	22-1/2"	15-1/4"	6-3/4"	\$71.99



MOGUL-BASE TEMPLIGHT FIXTURE WITH 6 FT. CORD

- Weight: 4 lbs.
- Std. Pkg: 1



ITEM	OVERALL HEIGHT	CAGE HEIGHT	CAGE DIAMETER	PRICE EACH
TLF-LW	22-1/2"	15-1/4"	6-3/4"	\$82.99



MOGUL-BASE TEMPLIGHT FIXTURE WITH 6 FT. CORD & STRIPPED LEADS

- Weight: 4 lbs.
- Std. Pkg: 1



ITEM	OVERALL HEIGHT	CAGE HEIGHT	CAGE DIAMETER	PRICE EACH
TLF-LWS	22-1/2"	15-1/4"	6-3/4"	\$82.99



MOGUL-BASE MAGNETIC TEMPLIGHT FIXTURE WITH 6 FT. POWER CORD

- Magnet: 90 lbs.
- Weight: 4 lbs.
- Std. Pkg: 1



ITEM	OVERALL HEIGHT	CAGE HEIGHT	CAGE DIAMETER	PRICE EACH
TLFLMAGW	22-1/2"	15-1/4"	6-3/4"	\$89.99

MINI TEMPLIGHT FIXTURES

MINI TEMPLIGHT

- Base: Medium
- Cage Height: 5-7/8"
- Cage Diameter: 4"
- Std. Pkg: 1



Item: TLM

\$17.99 Each

MINI TEMPLIGHT WITH 6 FT. POWER CORD

- Base: Medium
- Cage Height: 5-7/8"
- Cage Diameter: 4"
- Std. Pkg: 1




Item: TLMW

\$25.99 Each

MINI TEMPLIGHT STRINGER WITH MALE & FEMALE CORD ENDS

- Base: Medium
- Cage Height: 5-7/8"
- Cage Diameter: 4"
- Std. Pkg: 1



Item: TLMPT

\$29.99 Each

- String together with extension cords!
- Lifetime Guarantee

MINI MAGNETIC TEMPLIGHT FIXTURE WITH 6 FT. POWER CORD

- Base: Medium
- Magnet: 90 lbs. pull strength
- Std. Pkg: 1



Item: TLMAGW

\$19.99 Each

MEDIUM-BASE TEMPORARY LAMP SOCKET

- Rubber gland seals bulb base
- Pre-stripped wires allow easy install
- Std. Pkg: 10



Item: CLS

\$1.99 Each

TEMLIGHT ACCESSORIES

TEMLIGHT CEILING CLIP FOR HORIZONTAL MOUNTING

- Rugged steel clip
- Screws directly to ceiling surface



Item: TLMC

\$0.99 Each

TEMLIGHT SNAP HOOK

- EASY hanging from structural members
- Enhanced-strength carabiner
- Std. Pkg: 10



Item: TLH

\$3.99 Each

LOCKABLE CLEAR ACRYLIC TEMPLIGHT SHATTER GUARD

- Protects installed lamp
- Included padlocks deter bulb theft
- Std. Pkg: 1




Item: TLSGLK

\$7.99 Each

CLEAR ACRYLIC TEMPLIGHT SHATTER GUARD



- Protects installed lamp
- Quick zip-tie fastening
- Std. Pkg: 1



ITEM	PRICE EACH
TLSG	\$5.99

STEEL SNAP-ON SHATTER GUARD

- Protects installed lamp
- Snaps onto lamp-cage bottom
- Std. Pkg: 1





ITEM	PRICE EACH
TLSGW	\$4.99

TEMPLIGHT ACCESSORIES

SNAP-ON HORIZONTAL LAMP/BULB STABILIZER

- Supports horizontally-installed LED lamps
- Std. Pkg: 1



ITEM	PRICE EACH
TLHS	\$3.99

TEMPLIGHT LAMP/BULB TRANSPORT STABILIZERS

- Prevents bulb damage during transport
- Rigid foam holds lamp secure in fixture
- Std. Pkg: 50



ITEM	LAMP BASE	PRICE EACH
TLF-FC	Medium	\$1.99
TLF-FCL	Mogul	\$1.99

LAMP SOCKET ADAPTERS

- MOGADP converts mogul socket to accept medium bulbs
- MOGENLG converts medium socket to accept mogul bulbs
- Std. Pkg: 1



MOGADP




MOGENLG

ITEM	PRICE EACH
MOGADP	\$4.59
MOGENLG	\$9.99

TEMPLIGHT LIGHT-POLLUTION SHIELD


- Blocks light on one half of the fixture!
- Reflective interior finish
- Flexible & form-fitting



ITEM	FITS CAGE	HEIGHT	STD. PKG.	PRICE EACH
TLPS	TLF	13"	1	\$9.99
TLPS-L	TLF-L	15"	1	\$9.99

4" SQUARE "HANDS-FREE" SWIVEL FIXTURE HANGER

- Fits conduit: 1/2" or 3/4"
- Swings 20° from vertical
- Hinged door allows easy, hands-free wiring
- Std. Pkg: 25




Item: SC-5075HF



\$13.99 Each

4" SQUARE SOLID SWIVEL FIXTURE HANGERS

- Fits conduit: 1/2" or 3/4"
- Swings 20° from vertical
- Std. Pkg: 25



Item: SC-50 (1/2" Conduit)
Item: SC-75 (3/4" Conduit)



\$9.99 Each

4" SQUARE WEATHERPROOF SWIVEL FIXTURE HANGER

- Gasketed cover provides vapor-tight seal on box
- Fits conduit: 1/2" or 3/4"
- Swings 20° from vertical
- Std. Pkg: 25



Item: SC-50-VT

\$13.99 Each

4" SQUARE "SAFETY-GROUND" SWIVEL FIXTURE HANGER

- Fits conduit: 1/2" or 3/4"
- Swings 20° from vertical
- Ground wire connects pivot ball to cover
- Std. Pkg: 25



Item: GSC-5075

\$11.99 Each

FIXTURE HANGERS

4" SQUARE STAINLESS STEEL SWIVEL FIXTURE HANGER

- Gasketed cover provides vapor-tight seal
- Fits conduit: 1/2" or 3/4"
- Swings 20° from vertical
- Std. Pkg: 25



Item: SC-50-VTSS

\$21.99 Each

4" SQUARE WHITE SWIVEL FIXTURE HANGER

- Fits conduit: 1/2" or 3/4"
- Swings 20° from vertical
- Std. Pkg: 25



Item: SC-5075WH

\$12.99 Each

4" SQUARE BLACK SWIVEL FIXTURE HANGER

- Fits conduit: 1/2" or 3/4"
- Swings 20° from vertical
- Std. Pkg: 25



Item: SC-5075BK


\$12.99 Each

CALL FOR VOLUME DISCOUNTS!
847-455-0188

FIXTURE HANGERS

4" SQUARE GALVANIZED STATIONARY FIXTURE HANGERS

- Will not swing or rotate
- Std. Pkg: 25



ITEM	CONDUIT SIZE	PRICE EACH
52C50	1/2"	\$6.99
52C75	3/4"	\$7.99
52C100	1"	\$8.29
52C125	1-1/4"	\$8.79

4" SQUARE WHITE STATIONARY FIXTURE HANGERS


- Will not swing or rotate
- Great for cameras, occupancy sensors, horns & strobes
- Std. Pkg: 25



ITEM	CONDUIT SIZE	PRICE EACH
52C50-WH	1/2"	\$7.99
52C75-WH	3/4"	\$8.99
52C100-WH	1"	\$9.29
52C125-WH	1-1/4"	\$9.99

4" SQUARE-TO-ROUND UNIVERSAL FIXTURE RINGS

- Mounts any fixture or device
- Holes match 2.75" or 3.5" C-C
- Std. Pkg: 50




ITEM	RAISED	PRICE EACH
52C3-1/2U	1/2"	\$1.69
52C3-5/8U	5/8"	\$1.79
52C3-3/4U	3/4"	\$1.99



4" SQUARE-TO-ROUND PERFECT-FIT DEVICE RINGS

- Mount any device
- Holes align 2.75" C-C in any direction
- Std. Pkg: 25




ITEM	RAISED	PRICE EACH
EXR-F	Flat	\$2.09
EXR-1/2	1/2"	\$0.99
EXR-5/8	5/8"	\$1.09
EXR-3/4	3/4"	\$1.69
EXR-1	1"	\$3.49
EXR-1-1/4	1-1/4"	\$3.09
EXR-1-1/2	1-1/2"	\$4.09
EXR-2	2"	\$4.69



FIXTURE HANGERS

4" SQUARE-TO-OCTAGON DEVICE RING

- Extra space for LED drivers & wires
- Std. Pkg: 50




ITEM	RAISED	PRICE EACH
52C4-5/8	5/8"	\$3.59

- Call for additional raised depths!
- Patent pending

4-11/16" SQUARE "HANDS-FREE" SWIVEL FIXTURE HANGER

- Swings 20° & fits 1/2" or 3/4" threaded conduit
- Hinged door allows easy "hands-free" wiring
- Std. Pkg: 10



Item: **SC-507511BHF** **\$39.99** Each

4-11/16" SQUARE SOLID SWIVEL FIXTURE HANGER

- Fits conduit: 1/2" or 3/4"
- Swings 20° from vertical
- Std. Pkg: 10



Item: **SC-507511B**  **\$29.99** Each

4-11/16" SQUARE WEATHERPROOF SWIVEL FIXTURE HANGER

- Gasketed cover provides vapor-tight seal
- Fits conduit: 1/2" or 3/4"
- Swings 20° from vertical
- Std. Pkg: 10



Item: **SC-507511B-VT** **\$35.99** Each

4-11/16" SQUARE STAINLESS STEEL SWIVEL FIXTURE HANGER

- Gasketed cover provides vapor-tight seal
- Fits conduit: 1/2" or 3/4"
- Swings 20° from vertical
- Std. Pkg: 10




Item: SC-507511B-VTSS

\$45.99 Each

4" ROUND "HANDS-FREE" SWIVEL FIXTURE HANGER

- Fits conduit: 1/2" or 3/4"
- Swings 20° from vertical
- Hinged door allows easy "hands-free" wiring
- Std. Pkg: 25



Item: SC-5075HFR



\$13.99 Each

4" ROUND SOLID SWIVEL FIXTURE HANGERS

- Fits conduit: 1/2" or 3/4"
- Swings 20° from vertical
- Std. Pkg: 25



Item: SC-50R (1/2" Conduit)

Item: SC-75R (3/4" Conduit)



\$9.99 Each

4" ROUND SAFETY-GROUND SWIVEL FIXTURE HANGER

- Fits conduit: 1/2" or 3/4"
- Swings 20° from vertical
- Ground wire connects pivot ball to cover
- Std. Pkg: 25



Item: GSCR-5075

\$11.99 Each

FIXTURE HANGERS

4" ROUND WEATHERPROOF SWIVEL FIXTURE HANGER

- Gasketed cover provides vapor-tight seal
- Fits conduit: 1/2" or 3/4"
- Swings 20° from vertical
- Std. Pkg: 25



Item: SC-50R-VT

\$13.99 Each

4" ROUND STAINLESS STEEL SWIVEL FIXTURE HANGER

- Gasketed cover provides vapor-tight seal
- Fits stainless steel conduit: 1/2" or 3/4"
- Swings 20° from vertical
- Std. Pkg: 10



Item: SC-50R-VTSS

\$21.99 Each

4" ROUND WHITE SWIVEL FIXTURE HANGER

- Swings 20° from vertical
- Fits 1/2" or 3/4" conduit
- Std. Pkg: 25




Item: SC-5075RWH

\$12.99 Each

4" ROUND BLACK SWIVEL FIXTURE HANGER

- Swings 20° from vertical
- Fits 1/2" or 3/4" conduit
- Std. Pkg: 25



Item: SC-5075RBK

\$12.99 Each

FIXTURE HANGERS

4" OCTAGON GALVANIZED STATIONARY FIXTURE HANGERS

- Will not swing or rotate
- Std. Pkg: 25



ITEM	CONDUIT SIZE	PRICE EACH
54C50	1/2"	\$6.99
54C75	3/4"	\$7.99
54C100	1"	\$8.29
54C125	1-1/4"	\$8.99

4" OCTAGON WHITE STATIONARY FIXTURE HANGERS

- Will not swing or rotate
- Std. Pkg: 25



ITEM	CONDUIT SIZE	PRICE EACH
54C50-WH	1/2"	\$7.99
54C75-WH	3/4"	\$8.99
54C100-WH	1"	\$9.29
54C125-WH	1-1/4"	\$9.99


LIGHTING

GARVIN
ELECTRICAL MANUFACTURER

Need A Special Part Made?

WE CUSTOMIZE

Boxes & Covers | Fittings | Hangers & Clamps



Fast Solutions... Designed By You!

FIXTURE STEMS & CANOPY SETS

GALVANIZED RIGID NIPPLES

1/2"

ITEM	LENGTH	STD. PKG.	PRICE EACH
RN50C	Close	25	\$0.89
RN50150	1-1/2"	25	\$0.99
RN50200	2"	25	\$1.19
RN50300	3"	25	\$1.29
RN50400	4"	25	\$1.39
RN50500	5"	25	\$1.43
RN50600	6"	25	\$1.49
RN50800	8"	25	\$3.69
RN501000	10"	25	\$3.99
RN501200	12"	25	\$4.69



RN SERIES
2" to 12"



RN SERIES
CLOSE

CALL FOR CUSTOM SIZES!

3/4"

ITEM	LENGTH	STD. PKG.	PRICE EACH
RN75C	Close	25	\$1.09
RN75150	1-1/2"	25	\$1.29
RN75200	2"	25	\$1.35
RN75300	3"	25	\$1.59
RN75400	4"	25	\$1.79
RN75500	5"	25	\$1.89
RN75600	6"	25	\$1.99
RN75800	8"	25	\$3.99
RN751000	10"	25	\$4.89
RN751200	12"	25	\$5.39

1"

ITEM	LENGTH	STD. PKG.	PRICE EACH
RN100C	Close	25	\$1.69
RN100200	2"	25	\$1.89
RN100300	3"	25	\$1.99
RN100400	4"	25	\$2.39
RN100500	5"	25	\$2.69
RN100600	6"	25	\$2.89
RN100800	8"	25	\$4.99
RN1001000	10"	25	\$6.39
RN1001200	12"	25	\$7.29

1-1/4"

ITEM	LENGTH	STD. PKG.	PRICE EACH
RN125C	Close	25	\$2.09
RN125200	2"	25	\$2.19
RN125300	3"	25	\$2.59
RN125400	4"	25	\$3.09
RN125500	5"	25	\$3.29
RN125600	6"	25	\$3.49
RN125800	8"	25	\$6.69
RN1251000	10"	25	\$8.49
RN1251200	12"	25	\$9.99

1-1/2"

ITEM	LENGTH	STD. PKG.	PRICE EACH
RN150C	Close	25	\$2.59
RN150200	2"	25	\$2.69
RN150300	3"	25	\$3.29
RN150400	4"	25	\$3.99
RN150500	5"	25	\$4.59
RN150600	6"	25	\$4.79
RN150800	8"	25	\$8.39
RN1501000	10"	25	\$9.99
RN1501200	12"	25	\$10.99

2"

ITEM	LENGTH	STD. PKG.	PRICE EACH
RN200C	Close	25	\$3.09
RN200300	3"	25	\$3.99
RN200400	4"	25	\$4.99
RN200500	5"	25	\$5.99
RN200600	6"	25	\$6.89
RN200800	8"	12	\$9.99
RN2001000	10"	10	\$11.99
RN2001200	12"	10	\$13.49

2-1/2"

ITEM	LENGTH	STD. PKG.	PRICE EACH
RN250C	Close	10	\$5.89
RN250300	3"	10	\$6.49
RN250400	4"	10	\$7.69
RN250500	5"	10	\$9.29
RN250600	6"	10	\$10.39
RN250800	8"	10	\$13.19
RN2501000	10"	5	\$15.69
RN2501200	12"	5	\$17.19

3"

ITEM	LENGTH	STD. PKG.	PRICE EACH
RN300C	Close	10	\$6.99
RN300300	3"	10	\$7.49
RN300400	4"	10	\$9.19
RN300500	5"	10	\$10.99
RN300600	6"	10	\$12.19
RN300800	8"	5	\$15.69
RN3001000	10"	5	\$18.49
RN3001200	12"	1	\$22.49

3-1/2"

ITEM	LENGTH	STD. PKG.	PRICE EACH
RN350C	Close	10	\$8.49
RN350400	4"	6	\$10.99
RN350500	5"	5	\$12.99
RN350600	6"	3	\$13.99
RN350800	8"	3	\$17.49
RN3501000	10"	3	\$20.39
RN3501200	12"	1	\$23.99

4"

ITEM	LENGTH	STD. PKG.	PRICE EACH
RN400C	Close	10	\$9.99
RN400400	4"	6	\$11.99
RN400500	5"	5	\$14.49
RN400600	6"	5	\$15.49
RN400800	8"	3	\$19.99
RN4001000	10"	3	\$23.99
RN4001200	12"	1	\$28.99

**WHITE UNIVERSAL
CANOPY SET**

- Allows fixed or swivel stem mounting
- Use with 3/8" IPS stem
- Includes hardware & instructions
- Std. Pkg: 1



Item: LFCU **\$10.99** Each



**INCLUDED HARDWARE
SUPPORTS FIXED
OR SWIVEL MOUNTING!**

FIXTURE STEMS & CANOPY SETS

WHITE PENDANT FIXTURE STEMS - 3/8" IPS

- Use with canopy sets to mount lights and signs
- Std. Pkg: 1



**CALL FOR
CUSTOM LENGTHS
AND COLORS**

ITEM	LENGTH	PRICE EACH
LFS-375-12WH	12"	\$7.49
LFS-375-18WH	18"	\$8.99
LFS-375-24WH	24"	\$10.99
LFS-375-36WH	36"	\$15.99
LFS-375-48WH	48"	\$20.99
LFS-375-60WH	60"	\$25.99

FIXTURE-STEM COUPLER 3/8" THREADED

- Use with 3/8" IPS stems
- Color: White
- Std. Pkg: 1



Item: LFS-16WHT

\$4.99 Each

3/8" FIXTURE LOCKNUT

- Use with 3/8" IPS stems
- Zinc-plated steel
- Std. Pkg: 1



Item: LFS-375-NUT

\$0.89 Each

GARVIN
ELECTRICAL MANUFACTURER

Need A Special Part Made?

WE CUSTOMIZE

Boxes & Covers | Fittings | Hangers & Clamps



Fast Solutions... Designed By You!

CAN LIGHT CONVERSION COVERS

CONVERSION KIT FOR PENDANT-MOUNT FIXTURES

- Convert can lights to accept pendants
- FAST & EASY!
- Includes all mounting hardware!



Screw on crossbar.



Mount decorative trim ring.



Wire & install new pendant fixture.

ITEM	I.D. / O.D.	COLOR	STD. PKG.	PRICE EACH
CLC-800	3.75" / 8"	White	10	\$15.99

CEILING BLANK-UP COVERS

RECESSED CAN LIGHT BLANK-UP COVERS

- Covers unused can lights
- Multiple springs for various can depths
- White powder-coated steel
- Edge taper: 1/4"
- Std. Pkg: 25



ITEM	OUTSIDE DIAMETER	PRICE EACH
CBC-600	6"	\$13.99
CBC-800	8"	\$16.99
CBC-1200	12"	\$19.99



Remove trim & Screw in!




Attach spring!



Done!

DECORATIVE CEILING BOX TRIM RING

- Easily hides ugly wall imperfections around boxes/rings
- Color: White
- Std. Pkg: 25



ITEM	OUTSIDE DIAMETER	USE WITH	PRICE EACH
CBD-800	8"	Any boxes or rings in wall or ceiling	\$13.99
CBD-1200	12"		\$14.99



SLOPPY OVER-CUT



MISTAKE HIDDEN



CLEAN INSTALL

CEILING BLANK-UP COVERS

5" ROUND 2-3/4" C-C HOLES

- Color: White
- Std. Pkg: 25



ITEM	EDGE TAPER	HOLES C-C	MOUNTS TO	PRICE EACH
CBC-F	Flat	2-3/4"	Raised rings, 3-1/2" Round box, 3-1/2" Octagon box	\$2.99

5" ROUND 2-3/4" C-C HOLES

- Color: White
- Std. Pkg: 25



ITEM	EDGE TAPER	HOLES C-C	MOUNTS TO	PRICE EACH
CBC-275	1/4"	2-3/4"	Raised rings, 3-1/2" Round box, 3-1/2" Octagon box	\$2.79

5" ROUND 3-1/2" C-C HOLES

- Color: White
- Std. Pkg: 25



ITEM	EDGE TAPER	HOLES C-C	MOUNTS TO	PRICE EACH
CBC-350	1/4"	3-1/2"	4" Round box, 4" Octagon box	\$2.79

5" ROUND - UNIVERSAL FIT

- Color: White
- Std. Pkg: 25



ITEM	EDGE TAPER	HOLES C-C	MOUNTS TO	PRICE EACH
CBCU	1/4"	Centered w/ strap	All rings and boxes	\$2.79

8" ROUND 2-3/4" C-C HOLES

- Long screws included
- Edge taper: 1/4"
- Color: White
- Std. Pkg: 25



ITEM	HOLES C-C	MOUNTS TO	PRICE EACH
CBC-275800	2-3/4"	Raised rings, 3-1/2" Round box, 3-1/2" Octagon box	\$6.99

8" ROUND 3-1/2" C-C HOLES

- Long screws included
- Edge taper: 1/4"
- Color: White
- Std. Pkg: 25



ITEM	HOLES C-C	MOUNTS TO	PRICE EACH
CBC-350800	3-1/2"	4" Round box, 4" Octagon box	\$6.99

LIGHTING

Got A Product Idea!


WE CAN MAKE IT

Your Dream Can Become Reality!

CEILING BLANK-UP COVERS

DECORATIVE HOLE COVER

- Covers wall/ceiling holes or damaged areas
- Includes backer bar, setscrew & plate
- Color: White
- Std. Pkg: 25



ITEM	OUTSIDE DIAMETER	PRICE EACH
CBS-800	8"	\$9.99
CBS-1200	12"	\$16.99



SLIDE IN HOLE



TIGHTEN DOWN

HOOKS, CHAINS & HARDWARE

HIGH BAY FIXTURE HOOK

- 3/4" hub with locknut
- Setscrew prevents vibratory loosening
- Std. Pkg: 25



ITEM	PRICE EACH
CPMH1	\$4.99

HIGH BAY FIXTURE HOOK WITH RUBBER GASKET

- 3/4" hub with locknut & gasket
- Setscrew prevents vibratory loosening
- Great for damp locations
- Std. Pkg: 25



ITEM	PRICE EACH
CPMH1-VT	\$5.99

FIXTURE SUPPORT "JACK" CHAIN

- #12 single-loop fixture chain
- Zinc-plated
- Std. Pkg: 100 Ft. (1 CTN)




S-hook sold separately

ITEM	PRICE EACH
JC-100	\$29.99

"S" HOOK

- #12 gauge
- S-style hook
- Zinc-plated
- Std. Pkg: 100



ITEM	DESCRIPTION	PRICE EACH
SH-12	S Hook	\$0.12

CHICAGO PLENUM FIXTURE WHIPS/CONNECTORS

6 FT. AIR-TIGHT PLENUM WHIPS AND CONDUITS

- Wire Gauge: #14 Stranded
- Connectors included
- Std. Pkg: 25



ITEM	CONDUIT	NO. OF WIRES	WIRE COLOR	PRICE EACH
PWHP-72	3/8"	None - Empty	----	\$15.99
PWHP-2A		2	Black, White	\$18.99
PWHP-3A		3	Black, White, Green	\$21.99
PWHP-5	1/2"	None - Empty	----	\$19.99



CONDUIT



AIR-TIGHT PLENUM WHIP STRAIGHT CONNECTORS

- Rubber washer seals conduit
- Std. Pkg: 100



ITEM	TUBING SIZE	FITS KNOCKOUT	PRICE EACH
FMT-38	3/8"	1/2"	\$3.29
FMT-50	1/2"	1/2"	\$4.29



AIR-TIGHT PLENUM WHIP 90° BOX CONNECTORS

- Rubber washers ensure air-tight fit
- Std. Pkg: 100



ITEM	CONDUIT SIZE	PRICE EACH
FMT-3890	3/8"	\$5.49
FMT-5090	1/2"	\$5.99

SWITCH ACCESSORIES

TOGGLE SWITCH LOCK BRACKET

- Rugged steel
- Lock-holes diameter: 0.31"
- Std. Pkg: 10



(lock not included)

ITEM	COLOR	PRICE EACH
TOGLOK	Silver	\$2.99
TOGLOKRD	Red	\$3.29
TOGLOKWH	White	\$3.29

TAN DOOR-JAMB SWITCH KIT

- Includes box, plate, switch & wire leads
- Std. Pkg: 10



Item: **DJSK**

\$11.99 Each

WHITE DOOR-JAMB SWITCH KIT

- Includes box, plate, switch & wire leads
- Std. Pkg: 10




Item: **DJSKWH**

\$18.99 Each

CABLE TIES

SELF-CUTTING CABLE TIES

• Std. Pkg: 50



ITEM	LENGTH	COLOR	TENSILE STRENGTH	PRICE EACH
CT46-308UVBSC	8"	Black	50 Lbs.	\$0.11
CT46-308SC	8"	Natural	50 Lbs.	\$0.11
CT46-311UVBSC	11"	Black	50 Lbs.	\$0.16
CT46-311SC	11"	Natural	50 Lbs.	\$0.16
CT46-314UVBSC	14"	Black	50 Lbs.	\$0.17
CT46-314SC	14"	Natural	50 Lbs.	\$0.17

NO MORE CUTTING CABLE TIES!



TWIST



DONE!

MAGNETIC CABLE-TIE MOUNTING BASE

• Color: Black



ITEM	FITS CABLE TIES	PULL OUT STRENGTH	STD. PKG.	PRICE (10 PACK)
CTMBK	Std. Nylon	10 Lbs	10	\$24.99
CTMVBK	Velcro	30 Lbs	10	\$15.99

• Sold in 10-Packs only!



STAINLESS STEEL FOR WALL SURFACES



Includes snap-in cable retainer bar

ITEM	SIZE	CAT5E CABLE CAPACITY	STD. PKG.	PRICE EACH
JHK-12SS	3/4"	20	50	\$5.99
JHK-21SS	1-5/16"	40	50	\$10.99
JHK-32SS	2"	80	50	\$13.99
JHK-64SS	4"	300	25	\$25.99

STAINLESS STEEL WITH ANGLE BRACKET FOR OVERHEAD SURFACES



Includes snap-in cable retainer bar

ITEM	SIZE	CAT5E CABLE CAPACITY	STD. PKG.	PRICE EACH
JHK-12-ABSS	3/4"	20	50	\$8.99
JHK-21-ABSS	1-5/16"	40	50	\$13.99
JHK-32-ABSS	2"	80	50	\$16.99
JHK-64-ABSS	4"	300	25	\$29.99

STEEL FOR WALL SURFACES



ITEM	SIZE	CAT5E CABLE CAPACITY	STD. PKG.	PRICE EACH
JHK-12	3/4"	20	50	\$1.49
JHK-21	1-5/16"	40	50	\$1.99
JHK-32	2"	80	50	\$2.79
JHK-64	4"	300	25	\$5.49
JHK-84*	6"	450	25	\$8.99

*Not UL Listed



**NEW
6"
SIZE!**



Includes snap-in cable retainer bar

“J” HOOKS

MAGNETIC FOR METAL SURFACES




Includes snap-in cable retainer bar

ITEM	SIZE	CAT5E CABLE CAPACITY	PULL OUT STRENGTH	STD. PKG.	PRICE EACH
JHK-12MAG	3/4"	20	90 Lbs	50	\$3.99
JHK-21MAG	1-5/16"	40	90 Lbs	50	\$4.49
JHK-32MAG	2"	80	90 Lbs	50	\$4.99
JHK-64MAG	4"	300	90 Lbs	25	\$5.69
JHK-84MAG	8"	450	90 Lbs	25	\$6.29

MAGNETIC FOR OVERHEAD METAL SURFACES

- Pull-out strength: 90 Lbs.



Includes snap-in cable retainer bar

ITEM	SIZE	CAT5E CABLE CAPACITY	STD. PKG.	PRICE EACH
JHK-12ABMAG	3/4"	20	25	\$4.19
JHK-21ABMAG	1-5/16"	40	25	\$4.39
JHK-32ABMAG	2"	80	25	\$4.59
JHK-64ABMAG	4"	300	25	\$5.49

ANGLE BRACKET FOR OVERHEAD SURFACES



Includes snap-in cable retainer bar

ITEM	SIZE	CAT5E CABLE CAPACITY	STD. PKG.	PRICE EACH
JHK-12-AB	3/4"	20	50	\$1.99
JHK-21-AB	1-5/16"	40	50	\$2.69
JHK-32-AB	2"	80	50	\$2.99
JHK-64-AB	4"	300	25	\$5.99



WITH HAMMER-ON BEAM CLAMP



Includes snap-in cable retainer bar



ITEM	FITS BEAM THICKNESS	SIZE	CAT5E CABLE CAPACITY	STD. PKG.	PRICE EACH
JHK-12-HO	1/8" - 1/4"	3/4"	20	50	\$2.69
JHK-12-HO516	5/16" - 1/2"	3/4"	20	50	\$2.69
JHK-12-HO916	9/16" - 3/4"	3/4"	20	50	\$2.69
JHK-21-HO	1/8" - 1/4"	1-5/16"	40	50	\$2.99
JHK-21-HO516	5/16" - 1/2"	1-5/16"	40	50	\$2.99
JHK-21-HO916	9/16" - 3/4"	1-5/16"	40	50	\$2.99
JHK-32-HO	1/8" - 1/4"	2"	80	50	\$3.99
JHK-32-HO516	5/16" - 1/2"	2"	80	50	\$3.99
JHK-32-HO916	9/16" - 3/4"	2"	80	50	\$3.99
JHK-64-HO	1/8" - 1/4"	4"	300	25	\$5.99
JHK-64-HO516	5/16" - 1/2"	4"	300	25	\$5.99
JHK-64-HO916	9/16" - 3/4"	4"	300	25	\$5.99

WITH LIGHT-DUTY BEAM CLAMP



Includes snap-in cable retainer bar

ITEM	SIZE	CAT5E CABLE CAPACITY	STD. PKG.	PRICE EACH
JHK-12-BC1	3/4"	20	50	\$2.29

WITH 1/4-20 STAMPED STEEL BEAM CLAMP



Includes snap-in cable retainer bar



ITEM	SIZE	CAT5E CABLE CAPACITY	STD. PKG.	PRICE EACH
JHK-21-BC	1-5/16"	40	50	\$3.29
JHK-32-BC	2"	80	50	\$3.99
JHK-64-BC	4"	300	25	\$6.99

LOW VOLTAGE

“J” HOOKS

**WITH BAT WING FOR
THREADED ROD**




Item	Size	CAT5E CABLE CAPACITY	Preinstalled Attachment	STD. PKG.	PRICE EACH
JHK-12-BW2	3/4"	20	Wing clip for #12 to 1/4" Rod	50	\$2.49
JHK-21-BW2	1-5/16"	40	Wing clip for #12 to 1/4" Rod	50	\$2.99
JHK-21-BW6	1-5/16"	40	Wing clip for 3/8" Rod	50	\$2.99
JHK-32-BW2	2"	80	Wing clip for #12 to 1/4" Rod	50	\$3.59
JHK-32-BW6	2"	80	Wing clip for 3/8" Rod	25	\$3.59
JHK-64-BW2	4"	300	Wing clip for #12 to 1/4" Rod	25	\$7.49

MULTI-RUN J-HOOK “TREES”



ITEM	SIZE	NO. OF HOOKS	PRICE EACH
JHT-212	1-15/16"	2	\$4.99
JHT-214	1-15/16"	4	\$9.99
JHT-216	1-15/16"	6	\$15.99
JHT-322	2"	2	\$5.99
JHT-324	2"	4	\$11.99
JHT-326	2"	6	\$16.99
JHT-642	4"	2	\$12.99
JHT-644	4"	4	\$22.99
JHT-646	4"	6	\$26.99



CALL FOR VOLUME DISCOUNTS!
847-455-0188

FOR WALL SURFACES



**STOPS CABLE
SPILL OVER!**

ITEM	LOOP SIZE	CAT5E CABLE CAPACITY	STD. PKG.	PRICE EACH
CAT150-WM	1-1/2"	36	50	\$1.59
CAT200-WM	2"	71	50	\$1.79
CAT400-WM	4"	250	25	\$3.59

MAGNETIC FOR METAL SURFACES


- Pull strength: 90 Lbs.



ITEM	LOOP SIZE	CAT5E CABLE CAPACITY	STD. PKG.	PRICE EACH
CAT150-WMAG	1-1/2"	36	50	\$4.69
CAT200-WMAG	2"	71	50	\$4.99
CAT400-WMAG	4"	250	25	\$5.59

MAGNETIC FOR OVERHEAD METAL SURFACES

- Pull strength: 90 Lbs.




ITEM	SIZE	STD. PKG.	PRICE EACH
CAT150-MAG	1-1/2"	50	\$4.79
CAT200-MAG	2"	50	\$4.99
CAT400-MAG	4"	25	\$5.69

"G" HOOKS

WITH ANGLE BRACKET FOR OVERHEAD SURFACES



ITEM	SIZE	CAT5E CABLE CAPACITY	STD. PKG.	PRICE EACH
CAT150-AB	1-1/2"	36	50	\$1.69
CAT200-AB	2"	71	50	\$1.79
CAT400-AB	4"	250	25	\$3.69




Back-to-back



OR Individually

WITH 1/4-20 THREADED STUD



No fasteners required

ITEM	LOOP SIZE	CAT5E CABLE CAPACITY	STD. PKG.	PRICE EACH
CAT150	1-1/2"	36	50	\$1.49
CAT200	2"	71	50	\$1.69
CAT400	4"	250	25	\$2.99



Need A Special Part Made?

WE CUSTOMIZE

Boxes & Covers | Fittings | Hangers & Clamps



Fast Solutions... Designed By You!

MAGNETIC FOR HEAVY CABLE BUNDLE

- Pull strength: 90 Lbs.
- Zinc-plated steel
- Std. Pkg: 50



ITEM	LOOP SIZE	PRICE EACH
BRM150-HD	1-1/2"	\$3.99
BRM200-HD	2"	\$4.29
BRM400-HD	4"	\$5.99

MAGNETIC FOR LIGHT CABLE BUNDLE


- Pull strength: 15 Lbs.
- Std. Pkg: 100



ITEM	LOOP SIZE	COLOR	PRICE EACH
BRM75BK	3/4"	Black	\$1.89
BRM75WH	3/4"	White	\$1.89
BRM100BK	1"	Black	\$1.99
BRM100WH	1"	White	\$1.99
BRM125BK	1-1/4"	Black	\$2.09
BRM125WH	1-1/4"	White	\$2.09

STAINLESS STEEL FOR WET LOCATIONS


- 316 Stainless steel
- Leg thread: 1/4-20
- Std. Pkg: 100



ITEM	LOOP SIZE	CAT5E CABLE CAPACITY	PRICE EACH
BR-125-SS	1-1/4"	30	\$4.39
BR-150-SS	1-1/2"	42	\$4.69
BR-200-SS	2"	73	\$4.99
BR-400-SS	4"	250	\$5.99

BRIDLE RINGS

STEEL




ITEM	LOOP SIZE	LEG THREAD	CAT5E CABLE CAPACITY	STD. PKG.	PRICE EACH
BR-501024	1/2"	10-24	5	100	\$0.82
BR-751024	3/4"	10-24	10	100	\$0.89
BR-1001024	1"	10-24	20	100	\$0.65
BR-1251024	1-1/4"	10-24	30	100	\$1.19
BR-1501024	1-1/2"	10-24	42	100	\$1.19
BR-2001024	2"	10-24	73	100	\$1.29
BR-125	1-1/4"	1/4-20	30	100	\$0.85
BR-150	1-1/2"	1/4-20	42	100	\$0.89
BR-200	2"	1/4-20	73	100	\$0.99
BR-400	4"	1/4-20	250	50	\$2.29



STEEL WITH DATA-CABLE SADDLE

• Leg thread: 1/4-20




ITEM	LOOP SIZE	CAT5E CABLE CAPACITY	STD. PKG.	PRICE EACH
BR-150-WH	1-1/2"	42	100	\$1.99
BR-200-WH	2"	73	100	\$2.39
BR-400-WH	4"	250	25	\$3.99



STEEL WITH WOOD SCREW THREAD

• Std. Pkg: 100



ITEM	LOOP SIZE	CAT5E CABLE CAPACITY	PRICE EACH
BR-100-WS	1"	20	\$0.89
BR-125-WS	1-1/4"	30	\$0.99
BR-150-WS	1-1/2"	42	\$1.19
BR-200-WS	2"	73	\$1.49



BRIDLE RINGS

WOOD SCREW WITH DATA-CABLE SADDLE

- Std. Pkg: 50



ITEM	LOOP SIZE	PRICE EACH
BR-150-WHWS	1-1/2"	\$1.99
BR-200-WHWS	2"	\$2.39

HOLLOW-WALL BRIDLE RING SETS

- 1/4-20 threaded leg 3-1/2" long



ITEM	LOOP SIZE	CAT5E CABLE CAPACITY	STD. PKG.	PRICE EACH
BR-150-TW	1-1/2"	42	50	\$2.79
BR-200-TW	2"	73	50	\$2.99
BR-400-TW	4"	250	25	\$4.99



Toggle in...Tighten down



No tools required!

"QUICK-SHOT" FOR STEEL/CONCRETE

- Works with all powder & gas fastening guns
- Pre-assembled - ready to shoot




ITEM	LOOP SIZE	CAT5E CABLE CAPACITY	STD. PKG.	PRICE EACH
BR-150-SSC	1-1/2"	42	100	\$2.39
BR-200-SSC	2"	73	100	\$2.69
BR-400-SSC	4"	250	50	\$3.99



BRIDLE RINGS

“QUICK-SHOT” WITH DATA-CABLE SADDLE FOR STEEL/CONCRETE


- Works with all powder & gas fastening guns
- Pre-assembled - ready to shoot
- Std. Pkg: 100



ITEM	LOOP SIZE	PRICE EACH
BR-150-SSCWH	1-1/2"	\$3.89
BR-200-SSCWH	2"	\$3.99

SCREW-MOUNT

- Fast & quiet install
- Screw hole dia: 0.26"



ITEM	CABLE LOOP SIZE	CAT5E CABLE CAPACITY	STD. PKG.	PRICE EACH
BR-150NP	1-1/2"	42	100	\$2.29
BR-200NP	2"	73	100	\$2.59
BR-400NP	4"	250	50	\$3.79



SCREW-MOUNT WITH DATA-CABLE SADDLE

- Screw hole dia: 0.26"
- Std. Pkg: 100




ITEM	CABLE LOOP SIZE	PRICE EACH
BR-150NPWH	1-1/2"	\$3.49
BR-200NPWH	2"	\$3.99

SNAP-ON DATA-CABLE SADDLE - ONLY

- Plenum-rated saddle
- Std. Pkg: 50



SNAP ON




DATA CABLE READY

ITEM	FITS RING SIZE	PRICE EACH
BRS150	1-1/2"	\$1.69
BRS200	2"	\$2.09


DISTRIBUTION RINGS

METAL DISTRIBUTION "D" RINGS

- Mounting hole: 0.22"
- Std. Pkg: 50



ITEM	MATERIAL	CABLE I.D.	CAT5E CABLE CAPACITY	STD. PKG.	PRICE EACH
DST-200	Cast Metal	2"	75	50	\$1.89
DST-300		3"	150	50	\$2.29
DST-500		5"	250	25	\$2.69
DST-800	Steel	8"	425	25	\$4.99
DST-1200	Steel	12"	550	25	\$5.99



PLASTIC DISTRIBUTION "D" RINGS



ITEM	CABLE I.D.	MTG. HOLE DIA.	CAT5E CABLE CAPACITY	STD. PKG.	PRICE EACH
DST-200-P	2"	0.22"	75	50	\$1.29
DST-300-P	3"		150	50	\$1.39
DST-500-P	5"		250	25	\$1.69

"DROP-IN" DISTRIBUTION RINGS

- Cables drop in, won't splash out
- Mounting hole dia: 0.175"
- Std. Pkg: 100




ITEM	SUPPORT LOOP	PRICE EACH
17AB	7/8" x 1-1/2"	\$0.95
17BB	1" x 1-7/8"	\$0.99
17CB	1-3/8" x 2-3/4"	\$1.19

DISTRIBUTION RINGS

OPEN DISTRIBUTION RINGS


- Two-hole base prevents twisting
- Mounting hole dia: 0.22"
- Std. Pkg: 50



ITEM	DIMENSIONS	PRICE EACH
ODR-250	2" Deep x 2" High	\$1.69
ODR-350	3" Deep x 1-1/2" High	\$1.79
ODR-375	3" Deep x 3" High	\$1.89

BACKBOARD SPOOLS


- Std. Pkg: 100



ITEM	MOUNTING	COLOR	PRICE EACH
WDS	Mounting Hole Only	White	\$0.79
WDSWS	Molded-In Wood Screw	White	\$0.79
WDSMS	Molded-In 12-24 for Data Racks	Black	\$0.79

DRIVE RINGS

NAIL-ON



ITEM	SIZE	CAT5E CABLE CAPACITY	STD. PKG.	PRICE EACH
DRV-1/2	1/2"	5	50	\$0.13
DRV-5/8	5/8"	10	25	\$0.19
DRV-7/8	7/8"	30	25	\$0.29
DRV-1-1/4	1-1/4"	65	25	\$0.38
DRV-1-1/2	1-1/2"	90	25	\$0.69

SCREW-MOUNT




(Screw not included.)

ITEM	SIZE	CAT5E CABLE CAPACITY	STD. PKG.	PRICE EACH
DRS-1/2	1/2"	5	50	\$0.13
DRS-5/8	5/8"	10	25	\$0.21
DRS-7/8	7/8"	30	25	\$0.26
DRS-1-1/4	1-1/4"	65	25	\$0.36
DRS-1-1/2	1-1/2"	90	25	\$0.59

INSULATING BUSHINGS

EMT PLASTIC INSULATING BUSHINGS



Snap on before cable pull.



ITEM	SIZE	STD. PKG.	PRICE EACH
IB-50	1/2"	50	\$0.13
IB-75	3/4"	50	\$0.17
IB-100	1"	25	\$0.45
IB-125	1-1/4"	25	\$0.59
IB-150	1-1/2"	25	\$0.89
IB-200	2"	25	\$1.49
IB-250	2-1/2"	10	\$2.99
IB-300	3"	10	\$3.89
IB-350	3-1/2"	5	\$3.99
IB-400	4"	5	\$5.19

SPLIT EMT PLASTIC INSULATING BUSHINGS



Snap on before or after cable pull.

ITEM	SIZE	STD. PKG.	PRICE EACH
IBS-50	1/2"	50	\$0.49
IBS-75	3/4"	50	\$0.59
IBS-100	1"	25	\$0.99
IBS-125	1-1/4"	25	\$1.09
IBS-150	1-1/2"	25	\$1.49
IBS-200	2"	25	\$2.29
IBS-250	2-1/2"	10	\$2.99
IBS-300	3"	10	\$3.99
IBS-350	3-1/2"	5	\$4.89
IBS-400	4"	5	\$5.69

RIGID THREADED PLASTIC INSULATING BUSHINGS



For threaded conduit/ connectors




ITEM	SIZE	STD. PKG.	PRICE EACH
IBT-50	1/2"	100	\$0.14
IBT-75	3/4"	100	\$0.18
IBT-100	1"	50	\$0.35
IBT-125	1-1/4"	50	\$0.45
IBT-150	1-1/2"	50	\$0.69
IBT-200	2"	10	\$1.49
IBT-250	2-1/2"	10	\$3.09
IBT-300	3"	10	\$3.99
IBT-350	3-1/2"	10	\$5.99
IBT-400	4"	10	\$7.99
IBT-500	5"	10	\$9.99
IBT-600	6"	10	\$12.99

LOW VOLTAGE

INSULATING BUSHINGS

SPLIT THREADED RIGID PLASTIC INSULATING BUSHINGS



For threaded conduit/ connectors

ITEM	SIZE	STD. PKG.	PRICE EACH
IBTS-50	1/2"	50	\$0.32
IBTS-75	3/4"	50	\$0.37
IBTS-100	1"	25	\$0.51
IBTS-125	1-1/4"	25	\$0.57
IBTS-150	1-1/2"	25	\$0.83
IBTS-200	2"	25	\$1.42
IBTS-250	2-1/2"	10	\$2.19
IBTS-300	3"	10	\$2.63
IBTS-350	3-1/2"	10	\$4.13
IBTS-400	4"	10	\$5.05
IBTS-500	5"	10	\$16.49
IBTS-600	6"	10	\$19.79

STEEL INSULATING BUSHING FOR MC CABLE

- Soft-rolled inner lip screws into MC cable



ITEM	SIZE	STD. PKG.	PRICE EACH
FB-50	1/2"	50	\$1.19
FB-75	3/4"	25	\$1.49
FB-100	1"	25	\$1.69



METAL STUD GROMMET

- Quick snap-on design
- Std. Pkg: 100



ITEM	SIZE	PRICE EACH
G100	Universal Metal Stud Grommet	\$0.19



Got A Product Idea!

WE CAN MAKE IT

Your Dream Can Become Reality!

INSULATING BUSHINGS

PLASTIC KNOCKOUT BUSHING STAR CONFIGURATION


- Snaps in box K.O. hole
- Slits allow easy pull-through
- Protects cable from sharp box edges



ITEM	BOX K.O.	STD. PKG.	PRICE EACH
KOBS-50	1/2"	50	\$0.18
KOBS-75	3/4"	50	\$0.19

PLASTIC KNOCKOUT INSULATING BUSHING

- Snaps in box K.O. hole
- Protects low-voltage wiring from sharp box edges



ITEM	FOR K.O. OPENING	STD. PKG.	PRICE EACH
KOB-50	1/2"	50	\$0.15
KOB-75	3/4"	50	\$0.17
KOB-100	1"	50	\$0.26
KOB-125	1-1/4"	25	\$0.29
KOB-150	1-1/2"	25	\$0.35



RUBBER KNOCKOUT INSULATING BUSHING

- Fits: 1/2" K.O. opening
- Protects low-voltage wiring from sharp box edges
- Std. Pkg: 50



Item: **KOBR-50**




\$0.19 Each

LOW VOLTAGE

CABLE PROTECTION PLATES

HAMMER-ON


- 16g steel
- Attachment: Wood spikes



ITEM	LENGTH	STD. PKG.	PRICE EACH
SP-3	3"	100	\$0.18
SP-6	6"	50	\$0.39

PRESS-ON

- 16g steel
- Attachment: Peel & stick



ITEM	LENGTH	STD. PKG.	PRICE EACH
SP-3-MS	3"	100	\$0.39
SP-6-MS	6"	50	\$0.79

SCREW-ON


- 16g steel
- Std. Pkg: 50



ITEM	LENGTH	PRICE EACH
SP-9	9"	\$0.59
SP-12	12"	\$0.89
SP-18	18"	\$1.29
SP-24	24"	\$1.69

EXTRA-WIDE, SCREW-ON

- 16g steel
- Std. Pkg: 50




ITEM	DIMS.	PRICE EACH
SP-33	3" wide x 3" long	\$0.35
SP-36	3" wide x 6" long	\$0.58
SP-39	3" wide x 9" long	\$0.85
SP-312	3" wide x 12" long	\$1.29
SP-318	3" wide x 18" long	\$1.79
SP-324	3" wide x 24" long	\$2.39
SP-58	5" wide x 8" long	\$0.89
SP-512	5" wide x 12" long	\$1.49
SP-518	5" wide x 18" long	\$2.09
SP-524	5" wide x 24" long	\$3.39

MEDIA BOXES & WALLPLATES

DUAL-POWER MEDIA BOX - SINGLE RECEPTACLE

- Cut-in to hollow walls
- 15 Amp power outlet included
- Std. Pkg: 20



Item: **DPBNP**

\$13.49 Each

OVERSIZE DUAL-POWER MEDIA BOX - GFCI

- 7-5/8" high x 8-1/8" wide
- 15 Amp GFCI duplex included
- Cut in to hollow walls
- Std. Pkg: 20



Item: **DPBOSGFI**

\$39.99 Each

OVERSIZE DUAL-POWER MEDIA BOX - DUPLEX

- 7-5/8" high x 8-1/8" wide
- 15 Amp duplex outlet
- Cut in to hollow walls
- Std. Pkg: 20



Item: **DPBOSDUP**

\$17.49 Each

ONE-GANG STAR GROMMET PLATE

- 4-1/2" high x 2-3/4" wide
- Cut in to hollow walls
- Std. Pkg: 25



Item: **LVP1**

\$3.79 Each

ONE-GANG NOSE PLATE

- 4-5/8" high x 2-3/4" wide
- Cut in to hollow walls
- Std. Pkg: 25



Item: **LVP1NP**

\$1.99 Each

ONE-GANG EXTRA-WIDE NOSE PLATE

- 4-7/8" high x 3-1/4" wide
- Cut in to hollow walls
- Std. Pkg: 25



Item: **LVP1SH**

\$2.79 Each

ONE-GANG EXTRA-WIDE NOSE PLATE

- 4-7/8" high x 3-1/4" wide
- Cut in to hollow walls
- Std. Pkg: 25



Item: **LVP1DH**

\$2.79 Each

TWO-GANG STAR GROMMET PLATE

- 4-1/2" high x 5" wide
- Cut in to hollow walls
- Flexible star grommet feed-through
- Std. Pkg: 10



Item: **LVP2**

\$4.99 Each

MEDIA BOXES & WALLPLATES

TWO-GANG NOSE PLATE

- 4-1/2" H x 4-1/2" W
- Cut in to hollow walls
- Std. Pkg: 10




Item: LVP2NP

\$2.99 Each

THREE-GANG PULL-THROUGH WALLPLATE

- 4-1/2" H x 6-3/8" W
- Cut in to hollow walls
- Std. Pkg: 10



Item: LVP3NP

\$3.99 Each

DUAL-POWER BOX

- Steel shield separates power
- Knockouts: (16)1/2" & 3/4"
- Std. Pkg: 25




Item: DPB-2

\$3.99 Each

DUAL-POWER BOX WITH VERTICAL BRACKET FOR STUD WALLS

- Steel shield separates power
- Knockouts: (16)1/2" & 3/4"
- Std. Pkg: 25




Item: DPB-2F

\$3.99 Each

DUAL-POWER BOX FOR HOLLOW WALLS

- Steel shield separates power
- Knockouts: (16)1/2" & 3/4"
- Old-work clips
- Std. Pkg: 25



Item: DPB-20W

\$3.99 Each

HINGED STEEL LOW VOLTAGE BOX

- 8" L x 7" W x 3-1/2" D
- K.O.s: 1/2" on sides
- Std. Pkg: 1



Item: BW98

\$15.99 Each


MEDIA BOXES & WALLPLATES

BRASS POP-UP FLOOR BOX KIT - THREE DATA PORTS

- Adjustable-height box
- Data port faceplate only (accepts most RJ-45 brands)
- Std. Pkg: 1



ITEM	PRICE EACH
FBCVBR-3D-KIT	\$79.00




STAINLESS STEEL POP-UP FLOOR BOX KIT - THREE DATA PORTS

- Adjustable-height box
- Data port faceplate only (accepts most RJ-45 brands)
- Std. Pkg: 1



ITEM	PRICE EACH
FBCVSS-3D-KIT	\$79.00



BRASS POP-UP FLOOR BOX KIT - 20A DUPLEX & USB

- Pre-wired receptacle
- Adjustable-height box
- USB: 5.0 Vdc, 4.0 Amp
- Std. Pkg: 1



ITEM	PRICE EACH
FBCVBR-U-KIT	\$89.00



STAINLESS STEEL POP-UP FLOOR BOX KIT - 20A DUPLEX & USB

- Pre-wired receptacle
- Adjustable-height box
- USB: 5.0 Vdc, 4.0 Amp
- Std. Pkg: 1



ITEM	PRICE EACH
FBCVSS-U-KIT	\$89.00





LOW VOLTAGE

DEVICE BRACKETS

24" CEILING TILE SLIDER BRACKET

- 4" square tabs
- Std. Pkg: 20





← Slides to any position →

Item: CTB-24

\$8.99 Each

24" CEILING TILE SLIDER BRACKET WITH BOX

- Box: 4" square, 3-1/2" deep
- 1/2" & 3/4" K.O.S
- Std. Pkg: 20




← Slides to any position →

Item: CTB-244S

\$11.99 Each

4" SQUARE REMODEL RING

- Fits walls: 3/8" to 1-1/2"
- Fits devices: 4" square
- Perforated tabs pinch on wall
- Std. Pkg: 50



Item: WBF-4

\$3.99 Each

ONE-GANG DEVICE BRACKET

- Fits walls: 3/8" to 1-1/2"
- Fits devices: One gang
- Perforated tabs pinch on wall
- Std. Pkg: 100



Item: WBF-1




\$1.69 Each



ONE-GANG DEVICE BRACKET FOR STUD WALLS

- Steel thickness: 0.035"
- Raised: 1/2" or 5/8"
- Vertical or horizontal mount
- Std. Pkg: 50



Item: **SLR-1-EV**



\$1.19 Each

ONE-GANG HEAVY-DUTY DEVICE BRACKET FOR STUD WALLS

- Steel thickness: 0.0625"
- Vertical or horizontal mount

ITEM	RAISED	STD. PKG.	PRICE EACH
SLR-150	1/2"	50	\$1.79
SLR-158	5/8"	25	\$1.79
SLR-175	3/4"	25	\$1.99



ONE-GANG ADJUSTABLE DEPTH DEVICE BRACKET FOR STUD WALLS

- Telescoping ring adjusts from 5/8" to 1-1/4" raised
- Std. Pkg: 10




Item: **AMR-1-LV**

\$6.99 Each

TWO-GANG DEVICE BRACKET FOR HOLLOW WALLS

- Fits walls: 3/8" to 1-1/2"
- Fits devices: Two gang
- Perforated tabs pinch on wall
- Std. Pkg: 50



Cut hole.



Fold tabs in.



Install 3 screws.

Item: **WBF-2**



\$2.19 Each

DEVICE BRACKETS

TWO-GANG HEAVY-DUTY DEVICE BRACKETS FOR STUD WALLS



- Steel thickness: 0.0625"

ITEM	RAISED	STD. PKG.	PRICE EACH
SLR-250	1/2"	50	\$1.79
SLR-258	5/8"	25	\$1.79
SLR-275	3/4"	25	\$1.99



TWO-GANG ADJUSTABLE DEPTH DEVICE BRACKET FOR STUD WALLS

- Telescoping ring adjusts from 5/8" to 1-1/4" raised
- Std. Pkg: 10




Item: AMR-2-LV

\$8.99 Each

TWO-GANG DEVICE BRACKET FOR STUD WALLS

- Steel thickness: 0.035"
- Raised: 1/2" or 5/8"
- Std. Pkg: 50




Item: SLR-2-EV



\$1.59 Each

4" OCTAGON-TO-SQUARE ADAPTER

- Converts round/octagon boxes for 4S devices
- Threaded exterior holes fit 4" square devices
- Std. Pkg: 25





Item: 52C1-OCT

\$1.59 Each

4" SQUARE "HANDS-FREE" SWIVEL FIXTURE HANGER

- Fits conduit: 1/2" or 3/4"
- Swings 20° from vertical axis
- Allows hands-free wiring
- Std. Pkg: 25




Item: SC-5075HF

\$13.99 Each

4" SQUARE SOLID SWIVEL FIXTURE HANGERS

- Fits conduit: 1/2" or 3/4"
- Swings 20° from vertical
- Std. Pkg: 25



Item: SC-50 (1/2" Conduit)
Item: SC-75 (3/4" Conduit)

\$9.99 Each

4" SQUARE SAFETY-GROUND SWIVEL FIXTURE HANGER

- Fits conduit: 1/2" or 3/4"
- Swings 20° from vertical
- Ground wire connects pivot ball to cover
- Std. Pkg: 25



Item: GSC-5075

\$11.99 Each

4" SQUARE WEATHERPROOF SWIVEL FIXTURE HANGER

- Gasketed cover provides vapor-tight seal
- Fits conduit: 1/2" or 3/4"
- Swings 20° from vertical
- Std. Pkg: 25



Item: SC-50-VT

\$13.99 Each

DEVICE HANGERS

4" SQUARE STAINLESS STEEL SWIVEL FIXTURE HANGER

- Gasketed cover provides vapor-tight seal
- Fits conduit: 1/2" or 3/4"
- Swings 20° from vertical
- Std. Pkg: 25



Item: **SC-50-VTSS**

\$21.99 Each

4" SQUARE SWIVEL FIXTURE HANGER

- Fits conduit: 1/2" or 3/4"
- Swings 20° from vertical
- Painted white
- Std. Pkg: 25



Item: **SC-5075WH**

\$12.99 Each

4" SQUARE SWIVEL FIXTURE HANGER

- Fits conduit: 1/2" or 3/4"
- Swings 20° from vertical
- Painted black
- Std. Pkg: 25



Item: **SC-5075BK**

\$12.99 Each

4" SQUARE GALVANIZED STATIONARY FIXTURE HANGERS

- Will not swing or rotate
- Std. Pkg: 25

ITEM	CONDUIT SIZE	PRICE EACH
52C50	1/2"	\$6.99
52C75	3/4"	\$7.99
52C100	1"	\$8.29
52C125	1-1/4"	\$8.79



4" SQUARE WHITE STATIONARY FIXTURE HANGERS


- Will not swing or rotate
- Std. Pkg: 25

ITEM	CONDUIT SIZE	PRICE EACH
52C50-WH	1/2"	\$7.99
52C75-WH	3/4"	\$8.99
52C100-WH	1"	\$9.29
52C125-WH	1-1/4"	\$9.99



4" ROUND "HANDS-FREE" SWIVEL FIXTURE HANGER

- Fits conduit: 1/2" or 3/4"
- Swings 20° from vertical
- Hinged door allows hands-free wiring
- Std. Pkg: 25



Item: **SC-5075HFR**



\$13.99 Each

4" ROUND SOLID SWIVEL FIXTURE HANGERS

- Fits conduit: 1/2" or 3/4"
- Swings 20° from vertical
- Std. Pkg: 25



Item: **SC-50R** (1/2" Conduit)

Item: **SC-75R** (3/4" Conduit)



\$9.99 Each

4" ROUND SAFETY-GROUND SWIVEL FIXTURE HANGER

- Fits conduit: 1/2" or 3/4"
- Swings 20° from vertical
- Ground wire connects pivot ball to cover
- Std. Pkg: 25



Item: **GSCR-5075**

garvinindustries.com

\$11.99 Each

Order by 2:00 pm for Same Day Shipping

PHONE 847-455-0188

DEVICE HANGERS

4" ROUND WEATHERPROOF SWIVEL FIXTURE HANGER

- Gasketed cover provides vapor-tight seal
- Fits conduit: 1/2" or 3/4"
- Swings 20° from vertical
- Std. Pkg: 25



Item: SC-50R-VT

\$13.99 Each

4" ROUND STAINLESS STEEL SWIVEL FIXTURE HANGER

- Gasketed cover provides vapor-tight seal
- Fits conduit: 1/2" or 3/4"
- Swings 20° from vertical
- Std. Pkg: 10




Item: SC-50R-VTSS

\$21.99 Each

4" ROUND BLACK SWIVEL FIXTURE HANGER

- Swings 20° from vertical
- Std. Pkg: 25



Item: SC-5075RBK

\$12.99 Each

4" ROUND WHITE SWIVEL FIXTURE HANGER

- Swings 20° from vertical
- Std. Pkg: 25



ITEM	FITS CONDUIT	PRICE EACH
SC-5075RWH	1/2" or 3/4"	\$12.99



DEVICE HANGERS

4" OCTAGON STATIONARY GALVANIZED FIXTURE HANGERS


- Will not swing or rotate
- Std. Pkg: 25



ITEM	CONDUIT SIZE	PRICE EACH
54C50	1/2"	\$6.99
54C75	3/4"	\$7.99
54C100	1"	\$8.29
54C125	1-1/4"	\$8.99

4" OCTAGON STATIONARY WHITE FIXTURE HANGERS


- Will not swing or rotate
- Std. Pkg: 25




ITEM	CONDUIT SIZE	PRICE EACH
54C50-WH	1/2"	\$7.99
54C75-WH	3/4"	\$8.99
54C100-WH	1"	\$9.29
54C125-WH	1-1/4"	\$9.99

4-11/16" SQUARE "HANDS-FREE" SWIVEL FIXTURE HANGER

- Swings 20°
- Hinged door allows hands-free wiring
- Std. Pkg: 10



SWING IN



LOCK TAB & WIRE UP



TIGHTEN DOWN

Item: SC-507511BHF

\$39.99 Each

4-11/16" SQUARE SOLID SWIVEL FIXTURE HANGER

- Fits conduit: 1/2" or 3/4"
- Swings 20°
- Std. Pkg: 10



Item: SC-507511B



\$29.99 Each

DEVICE HANGERS

4-11/16" SQUARE SOLID WEATHERPROOF SWIVEL FIXTURE HANGER

- Gasketed cover provides vapor-tight seal
- Fits conduit: 1/2" or 3/4"
- Swings 20° from vertical
- Std. Pkg: 10



Item: **SC-507511B-VT**

\$35.99 Each

4-11/16" SQUARE STAINLESS STEEL SOLID SWIVEL FIXTURE HANGER

- Gasketed cover provides vapor-tight seal
- Fits conduit: 1/2" or 3/4"
- Swings 20° from vertical
- Std. Pkg: 10



Item: **SC-507511B-VTSS**


\$45.99 Each

GARVIN
ELECTRICAL MANUFACTURER

Need A Special Part Made?

WE CUSTOMIZE

Boxes & Covers | Fittings | Hangers & Clamps



Fast Solutions... Designed By You!

NM CABLE SUPPORT STRAP

- Secures NM or MC cable to wood or metal stud
- Easy fold-over strap requires no tools!
- Std. Pkg: 100



ITEM	LENGTH	CABLE SURFACE	STD. PKG.	PRICE EACH
CJ	6"	Steel	100	\$0.52



NM CABLE SUPPORT STRAP - RUBBER INSULATED

- Secures NM or MC cable to wood or metal stud
- Easy fold-over strap requires no tools!
- Std. Pkg: 100



ITEM	LENGTH	CABLE SURFACE	STD. PKG.	PRICE EACH
CJIN	6"	Insulated Rubber	100	\$0.69



SNAP-IN CONDUIT SUPPORTS

- Secures conduit to wood or metal stud
- Sets conduit to properly align with box knockouts
- Spring steel



ITEM	FOR CONDUIT	FOR BOX	STD. PKG.	PRICE EACH
CS812	1/2" & 3/4"	1-1/2" Deep	100	\$0.43
CS812D	1/2" & 3/4"	2-1/8" Deep	100	\$0.45
CS912D	1"	2-1/8" Deep	50	\$0.69



NAIL STRAPS

- Secures conduit to wood stud
- Steel
- Std. Pkg: 100



ITEM	EMT CONDUIT	RIGID CONDUIT	PRICE EACH
NS-50	1/2"	3/8"	\$0.09
NS-75	3/4"	1/2"	\$0.11
NS-100	1"	3/4"	\$0.18

SNAP-LOCK CONDUIT HANGER ASSEMBLY

- Black spring steel
- Conduit set-back aligns with box knockouts
- Std. Pkg: 100



ITEM	CONDUIT SIZE	PRICE EACH
MSCH-1234	1/2" or 3/4"	\$1.99
MSCH-1	1"	\$2.19

CABLE/CONDUIT

Surface Mount

STAINLESS STEEL ONE-HOLE STRAPS FOR EMT

- 316 Stainless steel




ITEM	SIZE	STD. PKG.	PRICE EACH
OHSS-38	3/8"	100	\$1.89
OHSS-50	1/2"	50	\$1.99
OHSS-75	3/4"	50	\$2.39
OHSS-100	1"	25	\$2.69
OHSS-125	1-1/4"	25	\$3.79
OHSS-150	1-1/2"	25	\$4.89
OHSS-200	2"	25	\$4.99
OHSS-250	2-1/2"	10	\$13.99
OHSS-300	3"	10	\$15.99
OHSS-350	3-1/2"	10	\$18.99
OHSS-400	4"	10	\$22.99



STEEL ONE-HOLE STRAPS FOR EMT

- Zinc-plated steel



ITEM	SIZE	STD. PKG.	PRICE EACH
OHS-38	3/8"	100	\$0.15
OHS-50	1/2"	100	\$0.07
OHS-75	3/4"	100	\$0.11
OHS-100	1"	50	\$0.13
OHS-125	1-1/4"	50	\$0.29
OHS-150	1-1/2"	25	\$0.31
OHS-200	2"	25	\$0.59
OHS-250	2-1/2"	25	\$1.49
OHS-300	3"	10	\$1.79
OHS-350	3-1/2"	10	\$2.99
OHS-400	4"	10	\$3.59



STAINLESS STEEL ONE-HOLE STRAPS FOR RIGID

- 316 Stainless steel




ITEM	SIZE	STD. PKG.	PRICE EACH
OHSSR-25	1/4"	100	\$1.99
OHSSR-38	3/8"	100	\$1.99
OHSSR-50	1/2"	50	\$1.99
OHSSR-75	3/4"	50	\$2.39
OHSSR-100	1"	25	\$2.69
OHSSR-125	1-1/4"	25	\$3.79
OHSSR-150	1-1/2"	25	\$4.89
OHSSR-200	2"	25	\$6.99
OHSSR-250	2-1/2"	10	\$13.99
OHSSR-300	3"	10	\$15.99
OHSSR-350	3-1/2"	10	\$18.99
OHSSR-400	4"	10	\$22.99



STEEL ONE-HOLE STRAPS FOR RIGID

- Zinc-plated steel




ITEM	SIZE	STD. PKG.	PRICE EACH
OHSR-50S	1/2"	100	\$0.09
OHSR-75S	3/4"	100	\$0.14
OHSR-100S	1"	50	\$0.39
OHSR-125S	1-1/4"	50	\$0.49
OHSR-150S	1-1/2"	25	\$0.55
OHSR-200S	2"	25	\$0.99
OHSR-250S	2-1/2"	25	\$1.45
OHSR-300S	3"	10	\$1.79
OHSR-350S	3-1/2"	10	\$2.99
OHSR-400S	4"	10	\$3.59



IRON ONE-HOLE STRAPS FOR RIGID

- Use with CLB- shown in next section




ITEM	SIZE	STD. PKG.	PRICE EACH
OHSR-38M	3/8"	50	\$0.33
OHSR-50M	1/2"	50	\$0.55
OHSR-75M	3/4"	50	\$0.69
OHSR-100M	1"	25	\$0.99
OHSR-125M	1-1/4"	25	\$1.99
OHSR-150M	1-1/2"	25	\$2.69
OHSR-200M	2"	25	\$3.99
OHSR-250M	2-1/2"	25	\$7.99
OHSR-300M	3"	10	\$8.99
OHSR-350M	3-1/2"	10	\$9.99
OHSR-400M	4"	10	\$11.99
OHSR-500M	5"	10	\$49.99
OHSR-600M	6"	10	\$69.99



CONDUIT CLAMP BACK SPACERS

- Use with OHSR- shown above
- Elevates surface-mounted conduit to align with box knockouts



ITEM	SIZE	STD. PKG.	PRICE EACH
CLB-50	1/2"	50	\$0.82
CLB-75	3/4"	50	\$0.99
CLB-100	1"	50	\$1.89
CLB-125	1-1/4"	25	\$2.49
CLB-150	1-1/2"	25	\$2.89
CLB-200	2"	25	\$5.39
CLB-250	2-1/2"	25	\$5.99
CLB-300	3"	25	\$6.99
CLB-350	3-1/2"	10	\$17.99
CLB-400	4"	10	\$24.99
CLB-500	5"	10	\$59.99
CLB-600	6"	10	\$79.99



UNIVERSAL PVC CLAMP BACK SPACER

- Stackable to elevate surface conduit
- Fits 1/2", 3/4" or 1" conduits
- Will not rust or corrode




Single Stack



Double Stack

Triple Stack

ITEM	SIZE	STD. PKG.	PRICE EACH
CLBU	1/2" to 1"	50	\$0.99



STAINLESS STEEL TWO-HOLE STRAPS FOR EMT

- 316 Stainless steel



ITEM	SIZE	STD. PKG.	PRICE EACH
THSS-38	3/8"	50	\$2.29
THSS-50	1/2"	50	\$2.39
THSS-75	3/4"	50	\$2.79
THSS-100	1"	25	\$3.29
THSS-125	1-1/4"	25	\$4.49
THSS-150	1-1/2"	25	\$5.69
THSS-200	2"	25	\$6.99
THSS-250	2-1/2"	25	\$16.99
THSS-300	3"	10	\$19.99
THSS-350	3-1/2"	10	\$22.99
THSS-400	4"	10	\$27.99




CABLE/CONDUIT

Surface Mount

STEEL TWO-HOLE STRAPS FOR EMT

- Zinc-plated steel



ITEM	SIZE	STD. PKG.	PRICE EACH
THS-25	1/4"	50	\$0.14
THS-38	3/8"	50	\$0.13
THS-50	1/2"	50	\$0.11
THS-75	3/4"	50	\$0.13
THS-100	1"	25	\$0.28
THS-125	1-1/4"	25	\$0.33
THS-150	1-1/2"	25	\$0.43
THS-200	2"	25	\$0.72
THS-250	2-1/2"	25	\$0.98
THS-300	3"	10	\$1.49
THS-350	3-1/2"	10	\$1.89
THS-400	4"	10	\$2.39



STAINLESS STEEL TWO-HOLE STRAPS FOR RIGID

- 316 Stainless steel



ITEM	SIZE	STD. PKG.	PRICE EACH
THSSR-50	1/2"	50	\$2.39
THSSR-75	3/4"	50	\$2.79
THSSR-100	1"	25	\$3.29
THSSR-125	1-1/4"	25	\$4.49
THSSR-150	1-1/2"	25	\$5.79
THSSR-200	2"	25	\$7.29
THSSR-250	2-1/2"	25	\$16.99
THSSR-300	3"	10	\$19.99
THSSR-350	3-1/2"	10	\$22.99
THSSR-400	4"	10	\$27.99



STEEL TWO-HOLE STRAPS FOR RIGID

- Zinc-plated steel



ITEM	SIZE	STD. PKG.	PRICE EACH
THSR-50	1/2"	50	\$0.16
THSR-75	3/4"	50	\$0.23
THSR-100	1"	50	\$0.30
THSR-125	1-1/4"	50	\$0.48
THSR-150	1-1/2"	50	\$0.59
THSR-200	2"	50	\$0.89
THSR-250	2-1/2"	25	\$0.99
THSR-300	3"	25	\$1.79
THSR-350	3-1/2"	25	\$1.89
THSR-400	4"	10	\$2.39
THSR-500	5"	10	\$23.99
THSR-600	6"	10	\$29.99



STAINLESS STEEL CONDUIT HANGERS

- 316 Stainless steel




ITEM	EMT CONDUIT	RIGID CONDUIT	STD. PKG.	PRICE EACH
CHSS-50	1/2"	3/8" or 1/2"	50	\$2.99
CHSS-75	3/4"	3/4"	25	\$3.09
CHSS-100	1"	1"	25	\$3.39
CHSS-125	1-1/4"	1-1/4"	25	\$3.49
CHSS-150	1-1/2"	1-1/2"	25	\$4.49
CHSS-175	----	1-1/2"	20	\$5.29
CHSS-200	2"	2"	10	\$6.99
CHSS-250	2-1/2"	2-1/2"	10	\$7.99
CHSS-300	3"	3"	10	\$8.99
CHSS-350	3-1/2"	3-1/2"	10	\$9.99
CHSS-400	4"	4"	10	\$16.99



CONDUIT HANGERS


- Zinc-plated steel



ITEM	EMT CONDUIT	RIGID CONDUIT	STD. PKG.	PRICE EACH
CH-50	1/2"	3/8" or 1/2"	50	\$0.29
CH-75	3/4"	1/2" or 3/4"	25	\$0.37
CH-100	1"	3/4"	25	\$0.39
CH-125	1-1/4"	1"	25	\$0.52
CH-150	1-1/2"	1-1/4"	25	\$0.55
CH-175	-----	1-1/2"	25	\$0.69
CH-200	2"	-----	25	\$0.79
CHR-200	-----	2"	25	\$0.79
CH-250	2-1/2"	2-1/2"	10	\$1.19
CH-300	3"	3"	10	\$1.59
CH-350	3-1/2"	3-1/2"	10	\$1.89
CH-400	4"	4"	5	\$2.99
CH-500	5"	5"	5	\$13.99

THREADED CONDUIT HANGERS

- Zinc-plated steel



Fastest install...NO NUTS!

ITEM	SIZE	STD. PKG.	PRICE EACH
CHQT-50	1/2"	50	\$0.15
CHQT-75	3/4"	25	\$0.19



QUICK-MOUNT SWING BOLT CONDUIT HANGERS

- Zinc-plated steel




SNAP ON CONDUIT, SWING IN BOLT!

ITEM	SIZE	STD. PKG.	PRICE EACH
CHQ-50	1/2"	50	\$0.35
CHQ-75	3/4"	25	\$0.45

PUSH-IN CONDUIT HANGERS

- Capacity: 25 Lbs.
- Zinc-plated spring steel
- Std. Pkg: 50




ITEM	EMT CONDUIT	HOLE SIZE	PRICE EACH
CHP-50	1/2"	9/32"	\$0.35
CHP-75	3/4"		\$0.41
CHP-100	1"		\$0.49

CABLE/CONDUIT

Surface Mount

PUSH-IN CONDUIT HANGER/ANGLE BRACKET ASSEMBLY

- Steel bracket & hanger
- Std. Pkg: 50




Conduit hanger rotates 360°

ITEM	EMT CONDUIT SIZE	PRICE EACH
CHPA-50	1/2"	\$1.10
CHPA-75	3/4"	\$1.29
CHPA-100	1"	\$1.69

SNAP-LOCK CONDUIT HANGERS

- Black spring steel




ITEM	CONDUIT SIZE	STD. PKG.	PRICE EACH
KC38T	3/8"	100	\$0.39
KC1234T	1/2" or 3/4"	100	\$0.49
KC1T	1"	50	\$0.69
KC114T	1-1/4"	50	\$0.69



SNAP-LOCK CONDUIT HANGER/ANGLE-BRACKET ASSEMBLY

- Steel bracket & hanger
- Std. Pkg: 50





Conduit hanger rotates 360°

ITEM	CONDUIT SIZE	PRICE EACH
BAKC38	3/8"	\$1.19
BAKC1234	1/2" or 3/4"	\$0.99



UNIVERSAL STRUT STRAPS FOR EMT OR RIGID CONDUIT



- Zinc-plated steel



ITEM	SIZE	STD. PKG.	PRICE EACH
STU50	1/2"	100	\$0.65
STU75	3/4"	100	\$0.69
STU100	1"	100	\$0.79
STU125	1-1/4"	50	\$0.95
STU150	1-1/2"	50	\$1.09
STU200	2"	50	\$1.29

EMT STRUT STRAPS


- Zinc-plated steel



ITEM	SIZE	STD. PKG.	PRICE EACH
STE50	1/2"	100	\$0.65
STE75	3/4"	100	\$0.75
STE100	1"	50	\$0.89
STE125	1-1/4"	50	\$0.99
STE150	1-1/2"	50	\$1.29
STE200	2"	50	\$1.79

STAINLESS STEEL STRUT STRAPS FOR RIGID CONDUIT



- 316 Stainless steel



ITEM	SIZE	STD. PKG.	PRICE EACH
STR50-SS	1/2"	100	\$3.79
STR75-SS	3/4"	100	\$4.39
STR100-SS	1"	100	\$4.99
STR125-SS	1-1/4"	100	\$5.99
STR150-SS	1-1/2"	100	\$7.49
STR200-SS	2"	100	\$8.79
STR250-SS	2-1/2"	100	\$9.99
STR300-SS	3"	100	\$11.99
STR350-SS	3-1/2"	100	\$14.99
STR400-SS	4"	100	\$18.99
STR500-SS	5"	25	\$22.99
STR600-SS	6"	25	\$26.99

RIGID STRUT STRAPS

- Zinc-plated steel




ITEM	SIZE	STD. PKG.	PRICE EACH
STR50	1/2"	100	\$0.65
STR75	3/4"	100	\$0.69
STR100	1"	50	\$0.79
STR125	1-1/4"	50	\$0.89
STR150	1-1/2"	50	\$0.99
STR200	2"	50	\$1.19
STR250	2-1/2"	50	\$1.29
STR300	3"	25	\$1.69
STR350	3-1/2"	25	\$1.99
STR400	4"	25	\$2.09
STR500	5"	25	\$2.99
STR600	6"	25	\$3.99

CABLE/CONDUIT

Strut Mount

ONE-PIECE STRUT CLAMPS (SOFT SADDLE)

- Soft, wide saddle supports cable, conduit & pipes
- Galvanized steel




ITEM	SIZE	STD. PKG.	PRICE EACH
OPCC-50	1/2"	100	\$1.49
OPCC-75	3/4"	100	\$1.59
OPCC-100	1"	50	\$1.69

*Supports cable
or conduits!*

ONE-PIECE STRUT CLAMPS (CONDUIT CRADLE)

- Zinc-plated steel



ITEM	EMT CONDUIT	RIGID CONDUIT	STD. PKG.	PRICE EACH
OPSC-38	3/8"	-----	100	\$1.19
OPSC-50	1/2"	-----	100	\$1.29
OPSC-75	3/4"	1/2"	50	\$1.39
OPSC-100	1"	3/4"	50	\$1.49
OPSC-125	1-1/4"	1"	50	\$1.69
OPSC-150	1-1/2"	1-1/4"	50	\$1.79
OPSC-200	2"	1-1/2"	50	\$1.89
OPSC-200R	-----	2"	25	\$2.69
OPSC-250	2-1/2"	2-1/2"	25	\$3.19
OPSC-300	3"	3"	25	\$4.19
OPSC-350	3-1/2"	3-1/2"	10	\$4.59
OPSC-400	4"	4"	10	\$5.69

ONE-PIECE STRUT CLAMPS (SETScrew)

- Setscrew locks conduit in place
- Twist-mount in strut channel
- Zinc-plated steel



ITEM	EMT CONDUIT	RIGID CONDUIT	STD. PKG.	PRICE EACH
OPS-50	1/2"	3/8"	100	\$0.99
OPS-75	3/4"	1/2"	50	\$1.09
OPS-100	1"	3/4"	50	\$1.19
OPS-125	1-1/4"	1"	50	\$1.29

CALL FOR VOLUME DISCOUNTS!
847-455-0188

CONDUIT HANGER/ BEAM CLAMP ASSEMBLY

- Beam clamp size: 1/4"
- Fits beam flange thickness to 1/2"
- Std. Pkg: 50




Conduit hanger rotates 360°

ITEM	EMT CONDUIT SIZE	RIGID CONDUIT SIZE	PRICE EACH
CHBC-50	1/2"	1/2"	\$1.69
CHBC-75	3/4"	3/4"	\$1.73
CHBC-100	1"	1"	\$1.79
CHBC-125	1-1/4"	----	\$1.85
CHBC-150	1-1/2"	1-1/4"	\$1.89
CHBC-175	----	1-1/2"	\$2.09
CHBC-200	2"	2"	\$2.39

PUSH-IN CONDUIT HANGER/BEAM CLAMP ASSEMBLY

- Load Capacity: 25 Lbs.
- 10-24 & 1/4-20 threaded holes
- Std. Pkg: 50




Conduit hanger rotates 360°

ITEM	EMT CONDUIT SIZE	PRICE EACH
CHP-50-TM	1/2"	\$1.96
CHP-75-TM	3/4"	\$1.99
CHP-100-TM	1"	\$2.09

PUSH-IN CONDUIT HANGER HAMMER-ON BEAM CLAMP ASSEMBLY - TOP MOUNT

- Load Capacity: 25 Lbs.
- 10-24 & 1/4-20 threaded holes
- Std. Pkg: 50



Conduit hanger rotates 360°

ITEM	EMT CONDUIT SIZE	BEAM FLANGE THICKNESS	PRICE EACH
CHO-5025-TM	1/2"	1/8" - 1/4"	\$1.43
CHO-5050-TM	1/2"	5/16" - 1/2"	\$1.62
CHO-5075-TM	1/2"	9/16" - 3/4"	\$1.96
CHO-7525-TM	3/4"	1/8" - 1/4"	\$1.60
CHO-7550-TM	3/4"	5/16" - 1/2"	\$1.72
CHO-7575-TM	3/4"	9/16" - 3/4"	\$2.10
CHO-10025-TM	1"	1/8" - 1/4"	\$1.61
CHO-10050-TM	1"	5/16" - 1/2"	\$1.76
CHO-10075-TM	1"	9/16" - 3/4"	\$1.99

CABLE/CONDUIT

Beam Mount

SNAP-LOCK CONDUIT HANGER/BEAM CLAMP ASSEMBLY - TOP MOUNT

- Steel clamp & hanger
- Fits beam flange: 1/2"
- Std. Pkg: 50




Conduit hanger rotates 360°

ITEM	CONDUIT SIZE	PRICE EACH
BCTM-5075	1/2" or 3/4"	\$1.99
BCTM-100	1"	\$1.99
BCTM-125	1-1/4"	\$2.29

SNAP-LOCK CONDUIT HANGER HAMMER-ON BEAM CLAMP ASSEMBLY

- Spring steel
- Std. Pkg: 50





Conduit hanger rotates 360°

ITEM	FITS FLANGE	CONDUIT SIZE	PRICE EACH
BC18KC38	1/8" to 1/4"	3/8"	\$1.79
BC18KC1234		1/2" or 3/4"	\$1.49
BC18KC1		1"	\$1.69
BC18KC114		1-1/4"	\$1.99
BC18KC112		1-1/2"	\$1.99
BC18KC2		2"	\$2.19
BC516KC38	5/16" to 1/2"	3/8"	\$1.89
BC516KC1234		1/2" or 3/4"	\$1.99
BC516KC1		1"	\$1.79
BC516KC114		1-1/4"	\$1.99
BC516KC112		1-1/2"	\$1.99
BC516KC2		2"	\$1.99



PUSH-IN CONDUIT HANGER/BEAM CLAMP ASSEMBLY - SIDE MOUNT

- Load capacity: 25 Lbs.
- Std. Pkg: 50





Conduit hanger rotates 360°

ITEM	EMT CONDUIT SIZE	PRICE EACH
CHP-50-SM	1/2"	\$1.96
CHP-75-SM	3/4"	\$1.69
CHP-100-SM	1"	\$2.10

PUSH-IN CONDUIT HANGER HAMMER-ON BEAM CLAMP ASSEMBLY - SIDE MOUNT

- Load Capacity: 15 Lbs.
- Std. Pkg: 50



Conduit hanger rotates 360°

ITEM	EMT CONDUIT SIZE	FITS BEAM FLANGE	PRICE EACH
CHO-5025-SM	1/2"	1/8" - 1/4"	\$1.26
CHO-5050-SM	1/2"	5/16" - 1/2"	\$1.32
CHO-5075-SM	1/2"	9/16" - 3/4"	\$1.69
CHO-7525-SM	3/4"	1/8" - 1/4"	\$1.28
CHO-7550-SM	3/4"	5/16" - 1/2"	\$1.38
CHO-7575-SM	3/4"	9/16" - 3/4"	\$1.78
CHO-10025-SM	1"	1/8" - 1/4"	\$1.43
CHO-10050-SM	1"	5/16" - 1/2"	\$1.30
CHO-10075-SM	1"	9/16" - 3/4"	\$1.69

SNAP-LOCK CONDUIT HANGER/ BEAM CLAMP ASSEMBLY - SIDE MOUNT

- Fits beam flange: 1/2"
- Std. Pkg: 50



Conduit hanger rotates 360°

ITEM	CONDUIT SIZE	PRICE EACH
BCSM-5075	1/2" or 3/4"	\$2.11
BCSM-100	1"	\$2.29
BCSM-125	1-1/4"	\$2.59

SNAP-LOCK CONDUIT HANGER/ HAMMER-ON BEAM CLAMP ASSEMBLY - SIDE MOUNT

- Zinc-plated spring steel
- Std. Pkg: 100




Conduit hanger rotates 360°

ITEM	FITS FLANGE	CONDUIT SIZE	PRICE EACH
BC18KC1234SM	1/8"	1/2" or 3/4"	\$1.19
BC18KC1SM	to 1/4"	1"	\$1.39



RIGHT-ANGLE UNDER-BEAM CONDUIT CLAMPS

- Galvanized iron & steel



ITEM	SIZE	STD. PKG.	PRICE EACH
RA50	1/2"	50	\$2.19
RA75	3/4"	50	\$2.29
RA100	1"	25	\$2.39
RA125	1-1/4"	25	\$2.69
RA150	1-1/2"	25	\$2.99
RA200	2"	10	\$3.99
RA250	2-1/2"	10	\$4.69
RA300	3"	10	\$5.99
RA350	3-1/2"	5	\$6.99
RA400	4"	5	\$7.99




CABLE/CONDUIT

Beam Mount

PARALLEL BEAM-EDGE CONDUIT CLAMPS


- Zinc-plated iron



ITEM	SIZE	STD. PKG.	PRICE EACH
PAR50	1/2"	50	\$3.99
PAR75	3/4"	50	\$4.99
PAR100	1"	50	\$5.29
PAR125	1-1/4"	25	\$7.49
PAR150	1-1/2"	25	\$8.69
PAR200	2"	25	\$10.99
PAR250	2-1/2"	10	\$12.99
PAR300	3"	10	\$13.99
PAR350	3-1/2"	10	\$14.99
PAR400	4"	10	\$16.99

CROSS BEAM-EDGE CONDUIT CLAMPS

- Zinc-plated iron



ITEM	CONDUIT SIZE	STD. PKG.	PRICE EACH
EDG50	1/2"	50	\$4.29
EDG75	3/4"	50	\$4.49
EDG100	1"	50	\$5.19
EDG125*	1-1/4"	25	\$6.29
EDG150*	1-1/2"	25	\$6.69
EDG200*	2"	25	\$8.99
EDG250*	2-1/2"	10	\$11.99
EDG300*	3"	10	\$14.59



*Not UL Listed

"J" STYLE UNDER-BEAM CONDUIT CLAMPS

- Zinc-plated iron



ITEM	CONDUIT SIZE	STD. PKG.	PRICE EACH
JCL50	1/2"	50	\$1.69
JCL75	3/4"	50	\$1.89
JCL100	1"	25	\$2.39
JCL125	1-1/4"	25	\$3.99
JCL150	1-1/2"	25	\$6.49
JCL250	2-1/2"	5	\$12.99
JCL350	3-1/2"	1	\$18.99

GARVIN
ELECTRICAL MANUFACTURER

Got A Product Idea!


WE CAN MAKE IT



Your Dream Can Become Reality!

PUSH-IN BACK-TO-BACK CONDUIT HANGERS

- Load capacity: 25 Lbs.
- Zinc-plated spring steel
- Std. Pkg: 50



Conduit hanger rotates 360°

ITEM	EMT(1) SIZE	EMT(2) SIZE	PRICE EACH
CHB-50	1/2"	1/2"	\$1.13
CHB-5075	1/2"	3/4"	\$1.19
CHB-50100	1/2"	1"	\$1.29
CHB-75	3/4"	3/4"	\$1.17
CHB-75100	3/4"	1"	\$1.26
CHB-100	1"	1"	\$1.33

SNAP-LOCK BACK-TO-BACK CONDUIT HANGERS

- Load Capacity: 100 Lbs.
- Zinc-plated spring steel
- Std. Pkg: 50



Conduit hanger rotates 360°

ITEM	EMT(1) SIZE	EMT(2) SIZE	PRICE EACH
KCB-50100	1/2" or 3/4"	1"	\$1.39
KCB-100100	1"	1"	\$1.59
KCB-100125	1"	1-1/4"	\$1.79

Rod Mount

UNIVERSAL DROP-ROD CONDUIT WING CLIPS


- Secures conduits/ cables to drop rod
- Fast install...no tools required
- Spring steel
- Std. Pkg: 100



ITEM	SUPPORTS CONDUIT			PRICE EACH
	EMT	RIGID	FLEXIBLE METAL	
CWC-38	3/8"	1/4"	3/8"	\$0.35
CWC-50	1/2"	3/8"	1/2"	\$0.34
CWC-75	3/4"	1/2"	3/4"	\$0.46
CWC-100	1"	3/4"	1"	\$0.48
CWC-125	1-1/4"	1"	1-1/4"	\$0.69

PUSH-IN CONDUIT HANGER/ WING-CLIP ASSEMBLY

- For rod size: 1/4"
- Spring steel
- Std. Pkg: 50



Conduit hanger rotates 360°


ITEM	EMT CONDUIT SIZE	ROD SIZE	PRICE EACH
CHPR-50	1/2"	1/4"	\$1.21
CHPR-75	3/4"		\$1.26
CHPR-100	1"		\$1.33

CABLE/CONDUIT

Rod Mount

SNAP-LOCK CONDUIT HANGER/WING-CLIP ASSEMBLY

- Spring steel
- Std. Pkg: 50



ITEM	CONDUIT SIZE	PRICE EACH
APSKC1234	1/2" & 3/4" conduit hanger & clip assembly.	\$0.99
APSKC1	1" conduit hanger & clip assembly.	\$0.99



BOX/CONDUIT HANGER WITH ROD/WIRE CLIP

- Zinc-plated steel
- For rod size: 1/4"
- Std. Pkg: 25



ITEM	EMT CONDUIT SIZE	PRICE EACH
BCRC	1/2" or 3/4"	\$3.29

Ceiling Grid Mount

PUSH-IN CONDUIT HANGER/ T-GRID CLIP ASSEMBLY

- Std. Pkg: 50



Conduit hanger rotates 360°

ITEM	EMT CONDUIT SIZE	PRICE EACH
CHPT-50	1/2"	\$1.23
CHPT-75	3/4"	\$1.29
CHPT-100	1"	\$1.41

SNAP-LOCK CONDUIT HANGER/T-GRID CLIP ASSEMBLY

- Steel clip & hanger
- Std. Pkg: 50



Conduit hanger rotates 360°

ITEM	CONDUIT SIZE	PRICE EACH
TC-5075	1/2" or 3/4"	\$0.89

HAMMER-ON CABLE PROTECTION PLATES


- .050" thick steel per NEC code



ITEM	LENGTH	WIDTH	STD. PKG.	PRICE EACH
SP-3	3"	1.5"	100	\$0.18
SP-6	6"	1.5"	50	\$0.39

PRESS-ON CABLE PROTECTION PLATES

- Easy peel & stick to studs
- .050" thick steel per NEC code



ITEM	LENGTH	WIDTH	STD. PKG.	PRICE EACH
SP-3-MS	3"	1.5"	100	\$0.39
SP-6-MS	6"	1.5"	50	\$0.79

SCREW-ON CABLE PROTECTION PLATES


- .050" thick steel per NEC code
- Std. Pkg: 50



ITEM	LENGTH	WIDTH	PRICE EACH
SP-9	9"	1.5"	\$0.59
SP-12	12"	1.5"	\$0.89
SP-18	18"	1.5"	\$1.29
SP-24	24"	1.5"	\$1.69

EXTRA-WIDE SCREW-ON CABLE PROTECTION PLATES

- .050" thick steel per NEC code
- Covers big bundles!
- Std. Pkg: 50




ITEM	DIMS.		PRICE EACH
	Width	Length	
SP-33	3"	3"	\$0.35
SP-36	3"	6"	\$0.58
SP-39	3"	9"	\$0.85
SP-312	3"	12"	\$1.29
SP-318	3"	18"	\$1.79
SP-324	3"	24"	\$2.39
SP-58	5"	8"	\$0.82
SP-512	5"	12"	\$1.49
SP-518	5"	18"	\$2.09
SP-524	5"	24"	\$3.39

BRACKETS

Adjustable - Stud Wall

ADJUSTABLE-LENGTH SCREW-GUN BRACKETS

- Galvanized steel
- Std. Pkg: 50




TELESCOPING SCREW GUN BRACKET IN WALL OPENING



ITEM	ADJUSTABLE LENGTH	BOX DEPTHS	STD. PKG.	PRICE EACH
BHA16	11" to 18"	1-1/2" to 2-1/8"	50	\$2.59
BHAD16		3" to 3-1/2"	50	\$3.99
BHA24	17" to 26"	1-1/2" to 2-1/8"	50	\$3.99
BHAD24		3" to 3-1/2"	50	\$4.99

BOX MOUNTING SLIDER BRACKET

- Galvanized steel
- Device ring secures bracket to box
- Std. Pkg: 50



BOX SLIDES BETWEEN STUDS FOR PERFECT POSITION IN WALL OPENING.



ITEM	FITS SQUARE BOX	STUD WALL CENTER DISTANCE	PRICE EACH
BMB16SL*	4", 4-11/16"	16"	\$3.99
BMB616SL	6"	16"	\$4.99

*Not UL Listed



ADJUSTABLE BAR HANGERS

- Galvanized steel
- Std. Pkg: 50





ITEM	STUD SPAN	MOUNTING	PRICE EACH
BHA1C	16" to 24"	Box-lock clip	\$2.99
BHA1		Box-lock clip & threaded stud	\$2.99

BRACKETS

Fixed-Position - Stud Wall

BOX MOUNTING BRACKETS FOR STANDARD DEVICE RINGS

- Zinc-plated steel
- Std. Pkg: 50




ITEM	FITS BOX SIZE	FAR SIDE STAND OFF	PRICE EACH
BB4-25	4" or 4-11/16" Square	2-1/2" or 3-5/8"	\$1.39
BB4-6	4" or 4-11/16" Square	2-1/2", 3-5/8", 5-1/2" or 6"	\$1.99



BOX MOUNTING BRACKET FOR ADJUSTABLE-DEPTH DEVICE RINGS

- Zinc-plated steel
- Std. Pkg: 50





ITEM	FITS BOX	SIDE STAND OFF	USE WITH	PRICE EACH
BMB1U	4" or 4-11/16" Square	2-1/2" or 3-5/8"	Adjustable-depth device rings: AMR1, AMR2 & AMR0	\$1.79



BOX MOUNTING BRACKETS FOR STANDARD DEVICE RINGS (DUAL STANDOFFS)

- Mounts on either side of stud




ITEM	FITS SQUARE BOX	FAR SIDE STAND OFF	STD. PKG.	PRICE EACH
BB4-26	4" or 4-11/16"	2-1/2" or 3-5/8"	25	\$1.39
BB6-26	6"	2-1/2" or 3-5/8"	50	\$2.99



3-POSITION BOX MOUNTING BRACKET FOR ADJUSTABLE DEPTH DEVICE RINGS

- Galvanized steel
- Std. Pkg: 25



ITEM	FITS BOX SIZE	STUD C - C	DESCRIPTION	PRICE EACH
BMB3U	4" or 4-11/16" Square	16"	Opening works with adjustable depth device rings: AMR1, AMR2 & AMR0	\$2.89





BRACKETS

Fixed-Position - Stud Wall

3-POSITION BOX MOUNTING BRACKET FOR STANDARD DEVICE RINGS



- Galvanized steel
- Std. Pkg: 25



ITEM	FITS SQUARE BOX	WALL STUD C-C	DESCRIPTION	PRICE EACH
BMB4S3P	4" or 4-11/16"	16"	Three box locations. Use HC nipples (HC-50, HC-75, HC-100) for prefab wall units.	\$2.89

4-POSITION BOX MOUNTING BRACKET FOR STANDARD DEVICE RINGS

- Galvanized steel
- Std. Pkg: 25



ITEM	FITS SQUARE BOX	STUDWALL SPACING	PRICE EACH
BMB4S4P	4" or 4-11/16"	24"	\$4.59

BOX FLOOR BRACKET FOR ADJUSTABLE-DEPTH DEVICE RINGS

- Galvanized steel
- Std. Pkg: 25



ITEM	FITS BOX	BOX CENTER OFF FLOOR	PRICE EACH
KP18AMR	4" or 4-11/16" Square	18"	\$3.99



BRACKETS


Low-Voltage - Stud Wall

ONE-GANG DEVICE BRACKET

- Fits walls: 3/8" to 1-1/2"
- Device openings: 1
- Perforated tabs pinch on wall
- Std. Pkg: 100



Item: WBF-1




\$1.69 Each



ONE-GANG LOW-VOLTAGE DEVICE BRACKET

- Zinc-plated steel




Mounts vertically or horizontally

ITEM	STEEL THICKNESS	RAISED	STD. PKG.	PRICE EACH
SLR-1-EV	.035"	1/2" or 5/8"	50	\$1.19



HEAVY-DUTY ONE-GANG LOW-VOLTAGE DEVICE BRACKET

- Zinc-plated steel




Mounts vertically or horizontally

ITEM	STEEL THICKNESS	RAISED	STD. PKG.	PRICE EACH
SLR-150	.0625"	1/2"	50	\$1.79
SLR-158	.0625"	5/8"	25	\$1.79
SLR-175	.0625"	3/4"	25	\$1.99



TWO GANG LOW-VOLTAGE DEVICE BRACKET FOR HOLLOW WALLS

- Fits walls: 3/8" to 1-1/2"
- Galvanized steel
- Std. Pkg: 50



Cut hole.



Fold tabs in.



Install 3 screws.



ITEM	WALL THICKNESS	PRICE EACH
WBF-2	3/8" to 1-1/2"	\$2.19

TWO-GANG LOW-VOLTAGE DEVICE BRACKET

- Zinc-plated 0.035" steel
- Std. Pkg: 50



Mounts vertically or horizontally




ITEM	RAISED	PRICE EACH
SLR-2-EV	1/2" or 5/8"	\$1.59

BRACKETS

Low-Voltage - Stud Wall

TWO-GANG HEAVY-DUTY LOW-VOLTAGE DEVICE BRACKETS

- Zinc-plated steel
- Steel thickness: 1/16"





Mounts vertically or horizontally

ITEM	RAISED	STD. PKG.	PRICE EACH
SLR-250	1/2"	50	\$1.79
SLR-258	5/8"	25	\$1.79
SLR-275	3/4"	25	\$1.99



4" SQUARE REMODEL RING FOR HOLLOW WALLS

- Galvanized steel
- Std. Pkg: 50



CUT & BEND



SECURE




INSTALL

ITEM	WORKS ON WALL THICKNESS	DEVICE OPENINGS	PRICE EACH
WBF-4	3/8" to 1-1/2"	4" Square	\$3.99

Switch Box Brackets

DEVICE LEVELER/RETAINER

- Zinc-plated steel
- Secures "floating" devices on wall
- Std. Pkg: 100



ITEM	HEIGHT	WIDTH	PRICE EACH
DLC	4.25"	2.30"	\$0.35

HOLLOW WALL SWITCHBOX SUPPORTS

- Galvanized steel
- Std. Pkg: 100 Pairs



SBS in use on backside of wall



ITEM	DESCRIPTION	PRICE
SBS	1-7/8" leg for standard thickness walls	\$0.49 PER PAIR
SBS-L	2-1/2" extra-long legs for thick walls	\$0.59 PER PAIR

BRACKETS

Ceiling Grid Brackets

24" LONG CEILING GRID BRACKET


- EASY snap-on design
- Std. Pkg: 50



ITEM	FIXED LENGTH	PRICE EACH
BHT1	24" ceiling grid T-bar bracket, used with boxes 1-1/2" or 2-1/8" deep.	\$6.99

24" LONG CEILING GRID BRACKET - HEIGHT ADJUSTABLE (0" - 8")


- EASY snap-on design
- Std. Pkg: 50



ITEM	DESCRIPTION	PRICE EACH
BHT1A	24" LONG ceiling grid T-bar bracket, adjustable up to 8" height.	\$11.99

48" LONG CEILING-GRID BRACKET - HEIGHT ADJUSTABLE (0" - 8")

- EASY snap-on design
- Std. Pkg: 25



ITEM	DESCRIPTION	PRICE EACH
BHT481A	48" Long ceiling grid T-bar bracket, adjustable up to 8" height above ceiling grid.	\$21.99

HEAVY DUTY T-GRID BRACKET

- Zinc-plated steel
- Std. Pkg: 25



ITEM	LENGTH	BOX DEPTH	LOAD CAPACITY	MTG. CLIP	PRICE EACH
BHT1HD	24"	1-1/2" or 2-1/8"	50 Lbs.	Yes	\$7.59


HANGING & SUPPORT

BRACKETS

Ceiling Grid Brackets

25" LONG RECESS DOWN LIGHT BRACKET



- Galvanized steel
- Std. Pkg: 25 Pairs



ITEM	DESCRIPTION	PRICE PER PAIR
BH3	25-1/4" straight bracket mounts architectural recess lights. Has notches 24" apart for use on a T-bar.	\$7.99

24" LONG CEILING TILE SLIDER BRACKET

- Mounting: 4" square tabs
- Slides to any position on tile
- Std. Pkg: 20





Item: **CTB-24**

\$8.99 Each

24" LONG CEILING TILE SLIDER BRACKET/ BOX ASSEMBLY

- 4" square box, 3-1/2" deep, 1/2" & 3/4" K.O.s
- Std. Pkg: 20




Item: **CTB-244S**

\$11.99 Each

4" SQUARE BOX WITH 4-WAY ADJUSTABLE CEILING-GRID BRACKET

- Galvanized steel




ITEM	SIDE K.O.S BOTTOM K.O.S	BOX DEPTH	STD. PKG.	PRICE EACH
52181-VTBAR	(4) 1/2" & (2) 3/4" (3) 1/2" & (2) 3/4"	3-1/2"	10	\$11.99

BRACKETS

Ceiling Grid Brackets

TOP-MOUNT T-GRID CLIP

- Galvanized steel
- Std. Pkg: 50



ITEM	HOLE SIZE	HOLE TYPE	PRICE EACH
TCAB	1/4"	Threaded	\$0.49

SIDE-MOUNT T-GRID CLIP


- Galvanized steel
- Std. Pkg: 50




ITEM	HOLE SIZE	HOLE TYPE	PRICE EACH
TCSM	1/4"	Threaded	\$0.49

CEILING GRID SWITCH BOX BRACKET

- Galvanized steel
- Std. Pkg: 25



1 REMOVE FLANGE.



2 SCREW TO GRID.



3 MOUNT BOX.



ITEM	DESCRIPTION	PRICE EACH
DCB	Mounting bracket to secure switch box to drop-ceiling grid	\$1.49

BRACKETS

Bar-Hanger Accessories

CLIP & SCREW SET FOR BH BAR HANGERS



- Std. Pkg: 50



ITEM	PRICE EACH
BHC	\$0.59

BOX CLIP & SCREW SET FOR BHT SERIES

- Steel
- Std. Pkg: 50




ITEM	USE WITH	PRICE EACH
BHTC	BHT1 and BHT1A.	\$0.52



Need A Special Part Made?

WE CUSTOMIZE

Boxes & Covers | Fittings | Hangers & Clamps





Fast Solutions... Designed By You!

BEAM CLAMPS

Standard Malleable Iron

IRON BEAM CLAMPS

- Zinc-plated iron
- Back & bottom threaded holes




ITEM	JAW OPENING	HOLE THREAD	LOAD (LBS)	STD. PKG.	PRICE EACH
MBC-1024	7/8"	10-24	375	100	\$1.49
MBC-1420	7/8"	1/4-20	450	50	\$0.79
MBC-3816	1-1/8"	3/8-16	1300	25	\$2.79
MBC-1213	1-3/8"	1/2-13	1700	10	\$4.99



STAINLESS STEEL MALLEABLE IRON BEAM CLAMPS

- 316 Stainless steel



ITEM	HOLE THREAD	STD. PKG.	PRICE EACH
MBC-1420-SS	1/4-20	50	\$19.99
MBC-3816-SS	3/8-16	25	\$35.99

WIDE-MOUTH IRON BEAM CLAMPS

- Zinc-plated iron
- Back/bottom threaded holes



ITEM	HOLE	LOAD (LBS)	STD. PKG.	PRICE EACH
MBC-1420WM	1/4-20	450	50	\$7.99
MBC-3816WM	3/8-16	1300	25	\$9.99
MBC-1213WM	1/2-13	1700	10	\$12.99



HUGE
3-1/8" JAW
OPENING!


HANGING & SUPPORT

BEAM CLAMPS

Standard Malleable Iron

SLIM-BODY IRON BEAM CLAMP

- Zinc-plated iron
- Back/bottom threaded holes
- Std. Pkg: 50




ITEM	JAW OPENING	HOLE	LOAD (LBS)	PRICE EACH
MBC-3816EV	13/16"	3/8-16	900	\$2.69



HEAVY-DUTY IRON BEAM CLAMP

- Zinc-plated iron
- Back/bottom threaded holes
- Std. Pkg: 10



ITEM	JAW OPENING	HOLE	LOAD (LBS)	PRICE EACH
MBC-1213XL	31/32"	1/2-13	1700	\$7.99




HEAVY-DUTY BODY!

Standard Stamped Steel

SPRING-STEEL BEAM CLAMP - LIGHT DUTY

- Back/bottom threaded holes
- Black-oxide steel
- Std. Pkg: 100




ITEM	JAW SIZE	HOLES BACK & BOTTOM	PRICE EACH
BC1	3/4"	10-24 & 1/4-20 plus 3/8" hole	\$0.89



STAINLESS STEEL BEAM CLAMPS

- Back/bottom threaded holes
- 316 Stainless steel



ITEM	JAW SIZE	HOLES BACK & BOTTOM	LOAD (LBS)	STD. PKG.	PRICE EACH
BC-1420-SS	19/32"	1/4-20	150	100	\$5.99
BC-3816-SS	15/16"	3/8-16	200	25	\$9.99




BEAM CLAMPS

Standard Stamped Steel

STEEL BEAM CLAMPS


- Back/bottom threaded holes
- Zinc-plated steel



ITEM	JAW SIZE	HOLES BACK & BOTTOM	LOAD (LBS)	STD. PKG.	PRICE EACH
BC-1024	0.59"	10-24	100	100	\$1.29
BC-1420	0.59"	1/4-20	100	100	\$0.79
BC-3816	15/16"	3/8-16	200	25	\$2.59



6-1/4" WIDE-MOUTH BEAM CLAMP



ITEM	JAW SIZE	HOLE THREAD	STD. PKG.	PRICE EACH
BC-1420-XWM	6.25"	1/4-20	20	\$11.99

SPANS THE WIDEST BEAMS!

STAINLESS STEEL REVERSIBLE BEAM CLAMP

- 304 Stainless steel
- Std. Pkg: 25



ITEM	JAW OPENING	HOLE THREAD	PRICE EACH
JFCS-3816SS	3/4"	3/8-16	\$10.99

Reversible Stamped Steel

STEEL REVERSIBLE BEAM CLAMP

- Zinc-plated steel
- Std. Pkg: 25



ITEM	JAW OPENING	HOLE THREAD	PRICE EACH
JFCS-3816	3/4"	3/8-16	\$1.09





H
A
N
G
I
N
G
&
S
U
P
P
O
R
T

FLANGE CLIPS

Hammer-On - Spring Steel

HAMMER-ON BEAM FLANGE CLAMP

- Black spring steel
- Std. Pkg: 100




ITEM	FLANGE	HOLE THREAD	PRICE EACH
BC18	1/8" to 1/4"	1/4-20	\$0.69
BC516	5/16" to 1/2"		\$0.79
BC916	9/16" to 3/4"		\$1.19



HAMMER-ON BEAM FLANGE CLAMP WITH 1/4-20 STUD

- Black spring steel
- Std. Pkg: 100



ITEM	FLANGE	HOLE THREAD	PRICE EACH
BC18ST	1/8" to 1/4"	1/4-20	\$0.79
BC516ST	5/16" to 1/2"		\$0.99
BC916ST	9/16" to 3/4"		\$1.29



HAMMER-ON BEAM FLANGE CLIP

- Zinc-plated spring steel
- Std. Pkg: 50



ITEM	FLANGE	LOAD (LBS)	PRICE EACH
BCX	3/32" - 9/64"	160	\$0.59
BCX18	1/8" - 1/4"	200	\$0.59
BCX516	5/16" - 1/2"		\$0.59
BCX916	9/16" - 3/4"		\$0.59

THREADED ROD HANGER/HAMMER-ON BEAM CLAMP ASSEMBLY

- Black spring steel




ITEM	FITS BEAM THICKNESS	ROD SIZE	STD. PKG.	PRICE EACH
R1814T	1/8" to 1/4"	1/4-20	100	\$1.09
R51614T	5/16" to 1/2"	1/4-20	100	\$1.09
R91614T	9/16" to 3/4"	1/4-20	100	\$1.29

BEAM CLAMPS

Reversible "C" Clamp - Malleable Iron

JUNIOR REVERSIBLE IRON BEAM CLAMPS


- Zinc-plated



ITEM	HOLE THREAD	JAW OPENING	STD. PKG.	PRICE EACH
JFC-1420	1/4-20	3/4"	50	\$1.29
JFC-3816	3/8-16	3/4"	25	\$0.99
JFC-1213	1/2-13	3/4"	25	\$1.69
JFC-5811	5/8-11	7/8"	25	\$2.99



REVERSIBLE BLACK IRON BEAM CLAMPS



ITEM	HOLE THREAD	JAW OPENING	STD. PKG.	PRICE EACH
MFC-3816	3/8-16	1-1/4"	25	\$1.79
MFC-1213	1/2-13	1-1/4"	25	\$2.39
MFC-5811	5/8-11	1-3/8"	25	\$4.39
MFC-3410	3/4-10	1-3/8"	25	\$4.39




HANGING & SUPPORT

GARVIN
ELECTRICAL MANUFACTURER

Need A Special Part Made?

WE CUSTOMIZE

Boxes & Covers | Fittings | Hangers & Clamps




Fast Solutions... Designed By You!

BEAM CLAMPS


Inline Rod Hanger - Malleable Iron

GALVANIZED IRON ROD-HANGER BEAM CLAMPS



ITEM	BOTTOM HOLE THREAD	JAW OPENING	STD. PKG.	PRICE EACH
MCC-3816	3/8-16	3/4"	25	\$2.19
MCC-1213	1/2-13	3/4"	25	\$2.49
MCC-5811	5/8-11	3/4"	25	\$5.79
MCC-3410	3/4-10	3/4"	25	\$4.89

BLACK IRON ROD-HANGER BEAM CLAMPS



ITEM	BOTTOM HOLE THREAD	JAW OPENING	STD. PKG.	PRICE EACH
MCC-3816BK	3/8-16	3/4"	25	\$1.99
MCC-1213BK	1/2-13	3/4"	25	\$2.39
MCC-5811BK	5/8-11	3/4"	25	\$4.89
MCC-3410BK	3/4-10	3/4"	25	\$4.79

GARVIN
ELECTRICAL MANUFACTURER

Got A Product Idea!

WE CAN MAKE IT




Your Dream Can Become Reality!

BEAM CLAMPS


Inline Rod Hanger - Stamped Steel

BLACK STEEL ROD-HANGER BEAM CLAMPS



ITEM	BOTTOM HOLE THREAD	JAW OPENING	STD. PKG.	PRICE EACH
SCC-3816BK	3/8-16	3/4"	25	\$2.29
SCC-1213BK	1/2-13	3/4"	25	\$1.69
SCC-5811BK	5/8-11	3/4"	25	\$3.99
SCC-3410BK	3/4-10	3/4"	25	\$5.79

STAINLESS STEEL ROD-HANGER BEAM CLAMPS



ITEM	BOTTOM HOLE THREAD	JAW OPENING	STD. PKG.	PRICE EACH
SCC-3816SS	3/8-16	3/4"	25	\$6.99
SCC-1213SS	1/2-13	3/4"	25	\$8.99
SCC-5811SS	5/8-11	3/4"	25	\$16.99
SCC-3410SS	3/4-10	3/4"	25	\$29.99

GALVANIZED STEEL ROD-HANGER BEAM CLAMPS



ITEM	BOTTOM HOLE THREAD	JAW OPENING	STD. PKG.	PRICE EACH
SCC-3816	3/8-16	3/4"	25	\$2.49
SCC-1213	1/2-13	3/4"	25	\$2.99
SCC-5811	5/8-11	3/4"	25	\$5.49
SCC-3410	3/4-10	3/4"	25	\$5.99

HANGING & SUPPORT

ROD HANGERS

Quick Shot Threaded Rod

“QUICK SHOT” THREADED ROD HANGERS

- Std. Pkg: 50



Shoot into metal, concrete or masonry!

THREADED ROD

ITEM	DROP ROD	OVERALL LENGTH	PRICE EACH
STF1424	1/4"-20	24"	\$2.99
STF1430	1/4"-20	30"	\$3.19
STF1436	1/4"-20	36"	\$3.39
STF1448	1/4"-20	48"	\$4.99

- Pre-assembled with concrete nail & washer

Call for Custom Lengths

“QUICK SHOT” THREADED-ROD COUPLER

- Std. Pkg: 50



ITEM	ROD COUPLER	OVERALL LENGTH	PRICE EACH
STF14	1/4"-20	6"	\$1.19

- Pre-assembled with concrete nail & washer

ROD HANGERS

Quick Shot Slick Rod

“QUICK SHOT” SLICK ROD HANGERS

- Std. Pkg: 50



Shoot into metal,
concrete or masonry!

SLICK ROD

ITEM	THREAD SIZE	OVERALL LENGTH	PRICE EACH
STF0024	No thread, smooth rod 1/4" Dia.	24"	\$2.89
STF0030	No thread, smooth rod 1/4" Dia.	30"	\$2.99
STF0036	No thread, smooth rod 1/4" Dia.	36"	\$3.39

- Pre-assembled with concrete nail & washer

Call for Custom Lengths

H
A
N
G
I
N
G
&
S
U
P
P
O
R
T


“QUICK-SCREW” THREADED-ROD COUPLER

- Coupler thread: 1/4"-20
- Overall length: 6"
- Std. Pkg: 50



“QUICK SHOT” THREADED HANGER CLIPS

- Std. Pkg: 100



ITEM	THREADED HOLE	PRICE EACH
TRH-1420	1/4-20	\$0.69
TRH-3816	3/8-16	\$0.75

Item: STF14NP **\$1.09** Each

ROD HANGERS

Threaded Fasteners

THREADED HANGER FOR WOOD

- Std. Pkg: 100



ITEM	HOLE THREAD	OVERALL LENGTH	PRICE EACH
SMY142W	1/4-20	2"	\$1.39
SMY382W	3/8-16	2-1/2"	\$1.39

THREADED ROD HANGERS FOR MASONRY/BRICK


- Zinc-plated steel
- Std. Pkg: 100



ITEM	HOLE THREAD	PRICE EACH
SMY141C	1/4-20	\$1.89
SMY381C	3/8-16	\$1.69

THREADED HANGER FOR SHEET METAL


- Std. Pkg: 100



ITEM	HOLE THREAD	OVERALL LENGTH	PRICE EACH
SMY141S	1/4-20	1"	\$1.49
SMY381S	3/8-16	1"	\$1.49

MOUNTING PLATE FOR "BANG-ON" THREADED DECK-INSERT HANGERS

- Perfectly positions & secures deck hangers
- Works with any brand threaded metal-deck inserts
- Std. Pkg: 25



NEVER LOSE A THREADED HANGER!




Item: BOP-164 **\$4.99** Each

ROD HANGERS

Rod Attachments

SLIP-TIGHT ROD NUT FOR THREADED-ROD



ITEM	ROD SIZE	STD. PKG.	PRICE EACH
SLN-3816	3/8-16	100	\$2.59

WALL-MOUNT THREADED ROD HANGERS


- Black-oxide & zinc-plated steel



ITEM	THREADED HOLE	STD. PKG.	PRICE EACH
R014T	1/4-20	100	\$0.89
R038T	3/8-16	100	\$0.89

ROD ANGLE BRACKETS

- Zinc-plated steel



ITEM	FOR ROD SIZE	THRU HOLE SIZE		STD. PKG.	PRICE EACH
		Small	Large		
BA-1/4	1/4"	.250	.250	100	\$0.38
BA-1/4-SS	1/4"	.250	.250	100	\$1.89
BAT-3/8	3/8"	.280"	.385"	100	\$0.39
BA-3/8-SS	3/8"	.280"	.385"	100	\$2.29

Tough Reinforced Corner!

MULTI-FUNCTION CLIP FOR PLAIN OR THREADED ROD

- Black-oxide spring steel



ITEM	CONDUIT SIZE	STD. PKG.	PRICE EACH
APS	Attaches to #12 wire to 3/8" rod. Provides #10-24 & 1/4"-20 mounting holes.	50	\$0.42



BAR-JOIST WASHERS

- Std. Pkg: 50




ITEM	BOLT SIZE	PRICE EACH
23WBJ	1/4"	\$0.22
24WBJ	3/8"	\$0.22

STRUT FITTINGS

Flat Plates

TWO-HOLE SPLICE PLATE

- 1/4" Thick
- Zinc-plated
- Std. Pkg: 50



Item: SFF30

\$0.79 Each

THREE-HOLE SPLICE PLATE

- 1/4" Thick
- Zinc-plated
- Std. Pkg: 25



Item: SFF31

\$1.89 Each

FOUR-HOLE SPLICE PLATE

- 1/4" Thick
- Zinc-plated
- Std. Pkg: 25



Item: SFF32

\$1.99 Each

TWO-HOLE PARALLEL SPLICE PLATE

- 1/4" Thick
- Zinc-plated
- Std. Pkg: 25



Item: SFF34

\$1.99 Each

THREE-HOLE CORNER PLATE - FLAT


- Hole diameter: 9/16"
- Hole C-C: 1-7/8"
- Std. Pkg: 25



ITEM	MATERIAL FINISH	PRICE EACH
SFF50	Zinc	\$4.79
SFF50-GN	Green	\$4.79

FOUR-HOLE CORNER PLATE - FLAT


- Hole diameter: 9/16"
- Hole C-C: 1-7/8"
- Std. Pkg: 20



ITEM	MATERIAL FINISH	PRICE EACH
SFF51	Zinc	\$6.99
SFF51-GN	Green	\$6.99

FOUR-HOLE TEE PLATE - FLAT

- Hole diameter: 9/16"
- Hole C-C: 1-7/8"
- Std. Pkg: 20



ITEM	MATERIAL FINISH	PRICE EACH
SFF60	Zinc	\$2.99
SFF60-GN	Green	\$2.99

CALL FOR VOLUME DISCOUNTS!
847-455-0188

STRUT FITTINGS

Angle Plates

ONE-HOLE CORNER ANGLE - STAINLESS STEEL

- 316 Stainless steel
- Std. Pkg: 50



Item: SFL11-SS

\$7.99 Each

TWO-HOLE CORNER ANGLE

- Hole diameter: 9/16"
- Zinc-plated steel
- Std. Pkg: 50



Item: SFL11

\$2.49 Each

TWO-HOLE CORNER ANGLE

- Hole diameter: 9/16"
- Painted green
- Std. Pkg: 50



Item: SFL11-GN

\$2.49 Each

TWO-HOLE "CROSS" CORNER ANGLE

- Zinc-plated steel
- Std. Pkg: 50




Item: SFL20

\$1.89 Each

THREE-HOLE CORNER ANGLE

- Zinc-plated steel
- Std. Pkg: 25



Item: SFL21

\$2.59 Each

THREE-HOLE "3-WAY" CORNER ANGLE

- Zinc-plated steel
- Std. Pkg: 25



Item: SFL30

\$2.49 Each

FOUR-HOLE CORNER ANGLE

- Hole diameter: 9/16"
- Zinc-plated steel
- Std. Pkg: 25



Item: SFL13

\$3.59 Each

FOUR-HOLE CORNER ANGLE

- Hole diameter: 9/16"
- Painted green
- Std. Pkg: 25



Item: SFL13-GN

\$3.59 Each

STRUT FITTINGS

Angle Plates

FOUR-HOLE "3-WAY" CORNER ANGLE

- 316 Stainless steel
- Std. Pkg: 25



Item: **SFL31-SS**

\$13.99 Each

FOUR-HOLE "3-WAY" CORNER ANGLE

- Zinc-plated steel
- Std. Pkg: 25



Item: **SFL31**

\$2.89 Each

TWO-HOLE 45° CORNER ANGLE

- Std. Pkg: 25



Item: **SFL60**

\$2.69 Each

FOUR-HOLE 45° CORNER ANGLE

- Std. Pkg: 25




Item: **SFL62**

\$3.99 Each

Strut-to-Beam Clamps

STRUT TO BEAM CLAMP - WINDOW

- Fits 1-5/8" strut
- Std. Pkg: 20



Item: **SFBC40**

\$7.39 Each

STRUT TO BEAM CLAMP WITH BOLT

- Fits 13/16" & 1-5/8" strut
- Std. Pkg: 25



Item: **SFBC60**

\$3.69 Each

STRUT TO BEAM CLAMP WITH BOLT

- Fits 2-7/16" & 3-1/4" strut
- Std. Pkg: 25



Item: **SFBC61**

\$3.89 Each

STRUT TO BEAM CLAMP - NOTCHED

- Std. Pkg: 50



Item: **SFBC70**

\$2.19 Each

STRUT FITTINGS

"U" Fittings

13/16" FOUR-HOLE U-FITTING SPLICE

- Hole diameter: 9/16"
- Length: 7-1/4"
- Channel depth: 13/16"
- Zinc-plated steel
- Std. Pkg: 10



Item: SFU33

\$8.99 Each

13/16" FOUR-HOLE U-FITTING SPLICE

- Hole diameter: 9/16"
- Length: 7-1/4"
- Channel depth: 13/16"
- Painted green
- Std. Pkg: 10



Item: SFU33-GN

\$8.99 Each

1-5/8" FOUR-HOLE U-FITTING SPLICE

- Hole diameter: 9/16"
- Length: 7-1/4"
- Channel depth: 1-5/8"
- Zinc-plated steel
- Std. Pkg: 10



Item: SFU32

\$8.99 Each

1-5/8" FOUR-HOLE U-FITTING SPLICE

- Hole diameter: 9/16"
- Length: 7-1/4"
- Channel depth: 1-5/8"
- Painted green
- Std. Pkg: 10



Item: SFU32-GN

\$8.99 Each

13/16" INSIDE STRUT JOINER

- Length: 4-7/16"
- Channel depth: 13/16"
- Zinc-plated steel
- Cam screws lock joiner in place
- Std. Pkg: 10



Item: SFEF33-1316

\$16.99 Each

1-5/8" INSIDE STRUT JOINER

- Length: 4-7/16"
- Channel depth: 1-5/8"
- Zinc-plated steel
- Cam screws lock joiner in place
- Std. Pkg: 10



Item: SFEF33-158

\$15.99 Each



WE CUT STRUT!

Any color...any length!


Call for a quote

STRUT FITTINGS

Post Bases

TWO-HOLE SINGLE-CHANNEL POST BASE

- Fits 1-5/8" strut
- Base: 4" x 6"
- Zinc-plated steel
- Std. Pkg: 5




Item: **SFP10**

\$11.99 Each

FOUR-HOLE SINGLE-CHANNEL POST BASE

- Fits 1-5/8" strut
- Base: 6" x 6"
- Zinc-plated steel
- Std. Pkg: 5



Item: **SFP13**

\$12.99 Each

FOUR-HOLE SINGLE-CHANNEL POST BASE

- Fits 1-5/8" strut
- Base: 6" x 6"
- Zinc-plated steel
- Std. Pkg: 5



Item: **SFP14**

\$8.99 Each

FOUR-HOLE SINGLE-CHANNEL POST BASE

- Fits 1-5/8" strut
- Base: 6" x 6"
- Painted green
- Std. Pkg: 5



Item: **SFP14-GN**

\$12.99 Each

Wall Brackets

WALL BRACKET CHANNEL

- For 1-5/8" strut
- Zinc-plated steel
- Std. Pkg: 1



ITEM	NO. OF MOUNTING HOLES	LENGTH	PRICE EACH
SFBR40-6	2	6"	\$9.99
SFBR40-9	2	9"	\$10.49
SFBR40-12	2	12"	\$10.99

End Caps

STRUT END CAP - PLASTIC

- Color: White
- Fits: 1-5/8" x 13/16" strut
- Std. Pkg: 100



Item: **SFEC08**

\$1.69 Each

STRUT END CAP - PLASTIC

- Color: White
- Fits: 1-5/8" x 1-5/8" strut
- Std. Pkg: 100



Item: **SFEC09**


\$1.99 Each

STRUT FITTINGS

Washers

“U” STRUT WASHERS


- Zinc-plated steel
- Std. Pkg: 50



ITEM	BOLT SIZE	PRICE EACH
SFU70-25	1/4"-20	\$1.29
SFU70-38	3/8"-16	\$1.29
SFU70-50	1/2"-13	\$1.29

STAINLESS STEEL STRUT WASHERS


- Outside diameter: 1-5/8"
- 316 Stainless steel 1/4" thick
- Std. Pkg: 100



ITEM	BOLT SIZE	PRICE EACH
SW-1/4-SS	1/4"	\$4.99
SW-3/8-SS	3/8"	\$4.99
SW-1/2-SS	1/2"	\$4.99
SW-5/8-SS	5/8"	\$4.99
SW-3/4-SS	3/4"	\$4.99

GREEN STRUT WASHERS


- Outside diameter: 1-5/8"
- Painted 1/4" thick steel
- Std. Pkg: 100



ITEM	BOLT SIZE	PRICE EACH
SW-1/4-G	1/4"	\$1.99
SW-3/8-G	3/8"	\$1.99
SW-1/2-G	1/2"	\$1.99
SW-5/8-G	5/8"	\$1.99

ZINC PLATED STRUT WASHERS

- Outside diameter: 1-5/8"
- Zinc-plated 1/4" thick steel
- Std. Pkg: 100




ITEM	BOLT SIZE	PRICE EACH
SW-1/4	1/4"	\$0.79
SW-3/8	3/8"	\$0.79
SW-1/2	1/2"	\$0.79
SW-5/8	5/8"	\$0.79
SW-3/4	3/4"	\$0.79

STRUT FITTINGS

Washers

NOTCHED STRUT WASHERS


- 1-5/8" O.D.
- Zinc-plated 1/4" thick steel
- Std. Pkg: 100



ITEM	BOLT SIZE	PRICE EACH
SFF20	1/4"	\$1.29
SFF21	3/8"	\$1.29
SFF22	1/2"	\$1.29
SFF23	5/8"	\$1.29
SFF24	3/4"	\$1.29

EXTRA-LARGE 2" SQUARE STRUT WASHERS

- Zinc-plated 1/4" thick steel
- Std. Pkg: 100



ITEM	BOLT SIZE	PRICE EACH
SW-2-3/8	3/8"	\$1.99
SW-2-1/2	1/2"	\$1.99
SW-2-5/8	5/8"	\$1.99
SW-2-3/4	3/4"	\$1.99

STAINLESS STEEL OCTAGON INSIDE-STRUT FLAT SLIDE WASHERS



- 1-1/2" O.D. fits in strut
- Std. Pkg: 100



ITEM	BOLT SIZE	PRICE EACH
12WFSS	1/4" or 3/16"	\$0.59
13WFSS	1/2"	\$0.59
14WFSS	3/8"	\$0.59

OCTAGON INSIDE-STRUT FLAT SLIDE WASHERS

- 1-1/2" O.D. fits in strut
- Std. Pkg: 100





ITEM	BOLT SIZE	PRICE EACH
12WFS	1/4" or 3/16"	\$0.22
13WFS	1/2"	\$0.22
14WFS	3/8"	\$0.22

STRUT FITTINGS

Nuts & Spring Nuts

SQUEEZE NUTS

• Std. Pkg: 100



ITEM	SIZE	PRICE EACH
SNSQ1420	1/4-20	\$0.89
SNSQ3816	3/8-16	\$0.99
SNSQ1213	1/2-13	\$0.99

CONE NUTS


• Std. Pkg: 100



ITEM	SIZE	PRICE EACH
SNCN1420	1/4-20	\$0.89
SNCN3816	3/8-16	\$0.99
SNCN1213	1/2-13	\$0.99

STRUT NUTS - NO SPRING


• Std. Pkg: 50



ITEM	HOLE THREAD	PRICE EACH
SNWO1420	1/4-20	\$0.42
SNWO3816	3/8-16	\$0.48
SNWO1213	1/2-13	\$0.59

SHORT-SPRING NUTS (FOR 0.813" & 1" SHALLOW STRUT)

• Std. Pkg: 50



ITEM	HOLE THREAD	PRICE EACH
SNSS1420	1/4-20	\$0.46
SNSS3816	3/8-16	\$0.49
SNSS1213	1/2-13	\$0.55

REGULAR SPRING NUTS (FOR 1.375" & 1.625" DEEP STRUT)

• Std. Pkg: 50



ITEM	HOLE THREAD	PRICE EACH
SNRS1420	1/4-20	\$0.36
SNRS3816	3/8-16	\$0.39
SNRS1213	1/2-13	\$0.45

LONG-SPRING NUTS (FOR 2.44" & 3.25" DEEP STRUT)

• Std. Pkg: 50



ITEM	HOLE THREAD	PRICE EACH
SNLS1420	1/4-20	\$0.47
SNLS3816	3/8-16	\$0.52
SNLS1213	1/2-13	\$0.56


HANGING & SUPPORT

SERVICE/UTILITY

Structural Attachments

WEDGE CLAMPS

- Aluminum / steel loop
- Reduces strain on sagging cables
- Std. Pkg: 10



ITEM	CABLE SIZES	PRICE EACH
CHOKR-1	#2 - #6 ACSR/AAAC	\$7.99
CHOKR-2	2/0 - 4/0 ACSR/AAAC	\$9.99

UTILITY SERVICE DROP FORKBOLT BRACKETS

- Hot-dipped galvanized
- Std. Pkg: 10



Attachment point on structure

ITEM	BOLT LENGTH	DESCRIPTION	PRICE EACH
FB	12"	Bolts through structure providing a secure attachment point for utility power line.	\$18.99
FBL	18"		\$28.99

UTILITY SERVICE DROP MOUNTING PLATE

- Hot-dipped galvanized
- Std. Pkg: 10



ITEM	SPECIAL FEATURES	PRICE EACH
SDP	Bolts to exterior of building structure providing attachment point for drop-wire clamps.	\$12.99

UTILITY POLE CONDUIT SUPPORT STAND-OFF BRACKET


- Hot-dipped galvanized
- Std. Pkg: 10



ITEM	SPECIAL FEATURES	PRICE EACH
SOB-1	Secures 2" to 6" conduit to utility pole. Clamping action stabilizes conduit on pole.	\$26.99

4-1/2" ROUND CONCRETE-TIGHT FLOOR BOX - SHALLOW

- Min. pour depth: 3.3"
- K.O.s: Sides: (8) 1/2" & 3/4"
- Mud cover prevents concrete from entering box
- Std. Pkg: 1



Item: FB330C

\$29.99 Each

4-1/2" ROUND CONCRETE-TIGHT FLOOR BOX - DEEP

- Min. pour depth: 4"
- K.O.s: Sides: (8) 1/2" & 3/4"
- Mud cover prevents concrete from entering box
- Std. Pkg: 1




Item: FB400C

\$34.99 Each

4-1/2" ROUND BRASS DUPLEX DEVICE COVER

- Outer Diameter: 5-3/4"
- Brushed brass
- Device covers with locking tab
- Std. Pkg: 1




Item: FBCVR-BR-FC



\$45.99 Each

4-1/2" ROUND STAINLESS STEEL DUPLEX DEVICE COVER

- Outer Diameter: 5-3/4"
- Brushed stainless
- Device covers with locking tab
- Std. Pkg: 1



Item: FBCVR-SS-FC



\$45.99 Each

FLOOR BOXES

Flush Mount

SINGLE-GANG BRASS FLOOR BOX KIT

- 20A Tamper-resistant duplex
- Locking tab: Yes
- Box depth: 3-1/2"
- Std. Pkg: 1

Item: **FBCVBR-1TR-KIT**



\$39.99 Each



SINGLE-GANG STAINLESS STEEL FLOOR BOX KIT

- 20A Tamper-resistant duplex
- Locking tab: Yes
- Box depth: 3-1/2"
- Std. Pkg: 1

Item: **FBCVSS-1TR-KIT**



\$39.99 Each



4-1/2" ROUND BRASS FLANGE

- Outer Diameter: 4-3/16"
- Std. Pkg: 1

Item: **FBF-BR**



\$16.99 Each

4-1/2" ROUND STAINLESS STEEL FLANGE

- Outer Diameter: 4-3/16"
- Std. Pkg: 1

Item: **FBF-SS**



\$16.99 Each

CALL FOR VOLUME DISCOUNTS!
847-455-0188

FLOOR BOXES

Flush Mount

4-1/2" ROUND STAINLESS STEEL CARPET FLANGE

- Outer Diameter: 5-1/8"
- Std. Pkg: 1




Item: FBCF-SS

\$19.99 Each

4-1/2" ROUND BRUSHED BRASS CARPET FLANGE

- Outer Diameter: 5-1/8"
- Std. Pkg: 1




Item: FBCF-BR

\$19.99 Each

FLOOR BOX DECORATIVE TRIM "GOOF" RING - BLACK

- Outer diameter: 6-1/2"
- Inner diameter: 5-1/4"
- Flange width: 5/8"
- Std. Pkg: 1



Covers gap of over-cut floors

ITEM	PRICE EACH
FBCVGRBK	\$2.99

CONDUIT BOXES

FLOOR BOXES

Pop-Up Kits

BRASS POP-UP FLOOR BOX KIT - 20A DUPLEX & USB

- Pre-wired receptacle
- Adjustable-height box included
- USB Ports: 5.0 Vdc, 4.0 Amp
- Std. Pkg: 1



Item: **FBCVBR-U-KIT**

\$89.00 Each

STAINLESS STEEL POP-UP FLOOR BOX KIT - 20A DUPLEX & USB

- Pre-wired receptacle
- Adjustable-height box included
- USB Ports: 5.0 Vdc, 4.0 Amp
- Std. Pkg: 1



Item: **FBCVSS-U-KIT**

\$89.00 Each

BRASS POP-UP FLOOR BOX KIT 20A TAMPER-RESISTANT GFCI

- Pre-wired receptacle
- Adjustable-height box included
- Std. Pkg: 1



Item: **FBCVBR-GTR-KIT**



\$99.00 Each

STAINLESS STEEL POP-UP FLOOR BOX KIT - 20A TAMPER-RESISTANT GFCI

- Pre-wired receptacle
- Adjustable-height box included
- Std. Pkg: 1



Item: **FBCVSS-GTR-KIT**



\$99.00 Each

FLOOR BOXES

Pop-Up Kits

BRASS POP-UP FLOOR BOX KIT 20A DUPLEX WEATHER/TAMPER RESISTANT DUPLEX

- Pre-wired receptacle
- Adjustable-height box included
- Std. Pkg: 1




Item: **FBCVBR-TRWR-KIT**



\$75.00 Each

STAINLESS STEEL POP-UP FLOOR BOX KIT - 20A WEATHER/ TAMPER RESISTANT DUPLEX

- Pre-wired receptacle
- Adjustable-height box included
- Std. Pkg: 1



Item: **FBCVSS-TRWR-KIT**



\$75.00 Each

BRASS POP-UP FLOOR BOX KIT - THREE DATA PORTS

- Adjustable-height box included
- Data port faceplate only (accepts std. RJ-45 brands)
- Std. Pkg: 1



Item: **FBCVBR-3D-KIT**



\$79.00 Each

STAINLESS STEEL POP-UP FLOOR BOX KIT - THREE DATA PORTS

- Adjustable-height box included
- Data port faceplate only (accepts std. RJ-45 brands)
- Std. Pkg: 1



Item: **FBCVSS-3D-KIT**




\$79.00 Each

CONCRETE SLAB BOXES

2" to 6" Deep


CONCRETE SLAB OCTAGON BOX ASSEMBLIES

- Pre-installed connectors & gasketed covers both sides
- Solid, leak-proof housing
- Rubber plugs seal unused connector holes
- Std. Pkg: 10



**Completely Assembled
Ready for Conduit!**

Patent Pending



LEAKPROOF BODY

GASKETED COVERS - BOTH SIDES

PRE-INSTALLED CONNECTORS

ITEM	GASKETED COVER	INSTALLED CONNECTORS	BOX DEPTH	PRICE EACH
OCA35050	Yes	(4) 1/2" Setscrew	3-1/2"	\$9.99
OCA35075	Yes	(4) 3/4" Setscrew	3-1/2"	\$9.99
OCA40050	Yes	(4) 1/2" Setscrew	4"	\$11.99
OCA40075	Yes	(4) 3/4" Setscrew	4"	\$11.99

CONCRETE SLAB BOXES

2" to 6" Deep

OCTAGON CONCRETE SLAB BOXES




FIG. 1



FIG. 2

1/2" & 3/4" K.O.S

ITEM	FIG #	BOX DEPTH	SIDE K.O.S	STD. PKG.	PRICE EACH
OCR-200	1	2"	(4) 1/2" & (4) 3/4"	10	\$5.99
OCR-250	1	2-1/2"	(4) 1/2" & (4) 3/4"	10	\$3.99
OCR-300	1	3"	(4) 1/2" & (4) 3/4"	10	\$4.49
OCR-350	2	3-1/2"	(8) 1/2" & (8) 3/4"	20	\$3.99
OCR-400	2	4"	(8) 1/2" & (8) 3/4"	5	\$4.09
OCR-400FAN Fan/Fixture Support	2	4"	(8) 1/2" & (8) 3/4"	5	\$22.99
OCR-500	2	5"	(8) 1/2" & (8) 3/4"	5	\$9.99
OCR-600	2	6"	(8) 1/2" & (8) 3/4"	5	\$13.99

3/4" & 1" K.O.S

OCR-300341*	1	3"	(4) 3/4" & (4) 1"	10	\$17.99
OCR-350341*	2	3-1/2"	(8) 3/4" & (8) 1"	5	\$18.49
OCR-400341*	2	4"	(8) 3/4" & (8) 1"	5	\$19.99



*Not UL Listed

CONDUIT BOXES

4" Square Concrete Slab Boxes

1/2" & 3/4" K.O.S 3-1/2" DEEP

- K.O.s sides: (4) 1/2", (4) 3/4"
- K.O.s bottom: Raised ground & concrete-tight K.O.s
- Std. Pkg: 10




Item: 52181-SPKR

\$6.99 Each

1/2" K.O.S 3-1/2" DEEP

- K.O.s sides: (8) 1/2"
- K.O.s bottom: Raised ground & concrete-tight K.O.s
- Std. Pkg: 10



Item: 52181-1/2-SPKR

\$6.99 Each

3/4" K.O.S 3-1/2" DEEP

- K.O.s sides: (8) 3/4"
- K.O.s bottom: Raised ground & concrete-tight K.O.s
- Std. Pkg: 10



Item: 52181-3/4-SPKRR

\$7.99 Each

3/4" K.O.S 3-1/2" DEEP

- K.O.s sides: (8) 3/4"
- K.O.s bottom: Raised ground & concrete-tight K.O.s
- Std. Pkg: 10



Item: 52181-3/4-SPKR

\$6.99 Each

4" SQUARE

1-1/4" / 1-1/2" Deep Boxes

1/2" K.O.S 1-1/4" DEEP

- K.O.s sides: (12) 1/2"
- K.O.s bottom: (5) 1/2"
- Std. Pkg: 50



Item: 52141-1/2

\$1.99 Each

1/2" K.O.S EXTENSION RING 1-1/4" DEEP

- K.O.s sides: (12) 1/2"
- Std. Pkg: 50



Item: 53141-1/2

\$4.49 Each

BLANK, NO K.O.S 1-1/2" DEEP

- Blank sides & bottom
- CALL FOR CUSTOM HOLE PLACEMENT!
- Std. Pkg: 50



Item: 52151-BLNK

\$5.99 Each

STAINLESS STEEL BLANK, NO K.O.S 1-1/2" DEEP

- 316 Stainless steel
- Blank sides & bottom
- CALL FOR CUSTOM HOLE PLACEMENT!
- Std. Pkg: 50



Item: 52151-BLNKSS

\$33.99 Each

1/2" K.O.S 1-1/2" DEEP

- K.O.s sides: (12) 1/2"
- K.O.s bottom: (4) 1/2"
- Std. Pkg: 50



Item: 52151-1/2

\$1.59 Each

1/2" K.O.S DRAWN CONSTRUCTION 1-1/2" DEEP

- K.O.s sides: (12) 1/2"
- K.O.s bottom: (4) 1/2"
- Std. Pkg: 50



Item: 52151-1/2DR

\$1.69 Each

3/4" K.O.S 1-1/2" DEEP

- K.O.s sides: (8) 3/4"
- K.O.s bottom: (3) 1/2", (2) 3/4"
- Std. Pkg: 50



Item: 52151-3/4

\$1.89 Each

3/4" K.O.S DRAWN CONSTRUCTION 1-1/2" DEEP

- K.O.s sides: (8) 3/4"
- K.O.s bottom: (3) 1/2", (2) 3/4"
- Std. Pkg: 50



Item: 52151-3/4DR

\$2.19 Each

4" SQUARE
1-1/2" Deep Boxes

3/4" AIR-TIGHT K.O.S
1-1/2" DEEP

- K.O.s sides: (8) 3/4"
- K.O.s bottom: (3) 1/2", (2) 3/4"
- Patented air-tight nail holes in bottom
- Std. Pkg: 50



Item: 52151-3/4-VT

\$6.39 Each

1/2" & 3/4" K.O.S
1-1/2" DEEP

- K.O.s sides: (8) 3/4"
- K.O.s bottom: (3) 1/2", (2) 3/4"
- Painted red
- Std. Pkg: 50



Item: 52151-3/4RED

\$3.99 Each

1/2" & 3/4" K.O.S
1-1/2" DEEP

- K.O.s sides: (6) 1/2", (6) 1/2"-3/4"
- K.O.s bottom: (3) 1/2", (2) 3/4"
- Std. Pkg: 50



Item: 52151-S

\$0.79 Each

1/2" & 3/4" K.O.S
DRAWN CONSTRUCTION
1-1/2" DEEP

- K.O.s sides: (6) 1/2", (6) 1/2"-3/4"
- K.O.s bottom: (3) 1/2", (2) 1/2"-3/4"
- Std. Pkg: 50



Item: 52151-SDR

\$1.19 Each

1/2" & 3/4" K.O.S
GROUND TAIL
1-1/2" DEEP

- Pre-installed 8" ground wire (12 ga) & 10-32 ground screw
- K.O.s sides: (6) 1/2", (6) 1/2"-3/4"
- K.O.s bottom: (3) 1/2", (2) 1/2"-3/4"
- Std. Pkg: 50



Item: 52151-SPT

\$2.19 Each

1/2" & 3/4" K.O.S
1-1/2" DEEP

- K.O.s sides: (6) 1/2", (6) 1/2"-3/4"
- K.O.s bottom: (2) 1/2", (2) 1/2"-3/4"
- Painted red
- Std. Pkg: 50



Item: 52151-RED

\$2.59 Each

1/2" & 3/4" AIR-TIGHT K.O.S
1-1/2" DEEP

- K.O.s sides: (8) 1/2", (4) 3/4"
- K.O.s bottom: (3) 1/2", (2) 3/4"
- Patented air-tight nail holes in bottom
- Std. Pkg: 50



Item: 52151-SVT

\$3.79 Each

1/2" & 3/4" AIR-TIGHT K.O.S
1-1/2" DEEP

- K.O.s sides: (8) 1/2", (4) 3/4"
- K.O.s bottom: (3) 1/2", (2) 3/4"
- Patented air-tight nail holes in bottom
- Painted red
- Std. Pkg: 50



Item: 52151-SVTRED

\$5.59 Each

**C
O
N
D
U
I
T

B
O
X
E
S**

4" SQUARE

1-1/2" Deep Boxes

STAINLESS STEEL 1/2" & 3/4" VAPOR-TIGHT K.O.S 1-1/2" DEEP

- 316 Stainless steel
- K.O.s sides: (8) 1/2", (4) 3/4"
- K.O.s bottom: (3) 1/2", (2) 3/4"
- Std. Pkg: 50



Item: 52151-SVTSS **\$33.99** Each

NM CABLE CLAMPS 1-1/2" DEEP

- K.O.s sides: (6) 1/2", (4) NM
- K.O.s bottom: (1) 1/2"
- Std. Pkg: 50



Item: 52151-R **\$3.99** Each

1/2" & 3/4" K.O.S CUT-IN BOX 1-1/2" DEEP

- K.O.s sides: (6) 1/2", (6) 1/2"-3/4"
- K.O.s bottom: (2) 1/2", (2) 3/4"
- Std. Pkg: 25



Item: 52151-OW **\$3.99** Each

MC/BX CABLE CLAMPS 1-1/2" DEEP

- K.O.s sides: (6) 1/2", (4) BX/MC
- K.O.s bottom: (1) 1/2"
- Std. Pkg: 50



Item: 52151-BX **\$1.99** Each

MC/BX CABLE CLAMPS CUT-IN BOX 1-1/2" DEEP

- K.O.s sides: (6) 1/2", (4) BX/MC
- K.O.s bottom: (1) 1/2"
- Std. Pkg: 25



Item: 52151-OWBX **\$4.29** Each

NM CABLE CLAMPS CUT-IN BOX 1-1/2" DEEP

- K.O.s sides: (6) 1/2", (4) NM
- K.O.s bottom: (1) 1/2"
- Std. Pkg: 25



Item: 52151-OWR **\$4.29** Each

GARVIN
ELECTRICAL MANUFACTURER

Need A Special Part Made?

WE CUSTOMIZE

Boxes & Covers | Fittings | Hangers & Clamps



Fast Solutions... Designed By You!

1/2" & 3/4" COMBO K.O.S
1-1/2" DEEP

- K.O.s sides: (4) 1/2", (5) 1/2"-3/4"
- K.O.s bottom: (3) 1/2", (2) 3/4"
- Bracket: Vertical right-angle
- Std. Pkg: 25



Item: 52151-AB

\$2.99 Each

3/4" K.O.S
1-1/2" DEEP

- K.O.s sides: (6) 3/4"
- K.O.s bottom: (3) 1/2", (2) 3/4"
- Bracket: Vertical right-angle
- Std. Pkg: 25



Item: 52151-3/4AB

\$3.59 Each

MC/BX CABLE CLAMPS

1-1/2" DEEP

- K.O.s sides: (4) MC/BX
- K.O.s bottom: (1) 1/2"
- Bracket: Vertical right-angle
- Std. Pkg: 25



Item: 52151-ABBX

\$3.99 Each

NM CABLE CLAMPS

1-1/2" DEEP

- K.O.s sides: (4) NM
- K.O.s bottom: (1) 1/2"
- Bracket: Vertical right-angle
- Std. Pkg: 25



Item: 52151-ABR

\$3.99 Each

1/2" K.O.S
1-1/2" DEEP

- K.O.s sides: (9) 1/2"
- K.O.s bottom: (3) 1/2", (2) 3/4"
- Bracket: Flat vertical
- Std. Pkg: 25



Item: 52151-F

\$1.39 Each

1/2" & 3/4" K.O.S
1-1/2" DEEP

- K.O.s sides: (6) 1/2", (3) 1/2"-3/4"
- K.O.s bottom: (3) 1/2", (2) 1/2"-3/4"
- Bracket: Flat vertical
- Std. Pkg: 25



Item: 52151-FS

\$1.29 Each

3/4" K.O.S
1-1/2" DEEP

- K.O.s sides: (6) 3/4"
- K.O.s bottom: (3) 1/2", (2) 3/4"
- Bracket: Flat vertical
- Std. Pkg: 25



Item: 52151-3/4F

\$2.79 Each

MC/BX CABLE CLAMPS
1-1/2" DEEP

- K.O.s sides: (2) 1/2", (1) 1/2"-3/4", (4) BX/MC
- K.O.s bottom: (1) 1/2"
- Bracket: Flat vertical
- Std. Pkg: 25



Item: 52151-FBX

\$2.79 Each

4" SQUARE

1-1/2" Deep Bracket Boxes

NM CABLE CLAMPS 1-1/2" DEEP

- K.O.s sides: (2) 1/2", (1) 1/2"-3/4", (4) NM
- K.O.s bottom: (1) 1/2"
- Bracket: Flat vertical
- Std. Pkg: 25



Item: 52151-FR

\$2.79 Each

1/2" & 3/4" K.O.S 1-1/2" DEEP

- K.O.s sides: (9) 1/2"
- K.O.s bottom: (2) 1/2", (2) 3/4"
- Bracket: Horizontal wood spike
- Std. Pkg: 25




Item: 52151-B

\$2.29 Each

MC/BX CABLE CLAMPS 1-1/2" DEEP

- K.O.s sides: (6) 1/2", (4) BX/MC
- K.O.s bottom: (1) 1/2"
- Bracket: Horizontal wood spike
- Std. Pkg: 25




Item: 52151-BBX

\$2.79 Each

NM CABLE CLAMPS 1-1/2" DEEP

- K.O.s sides: (2) 1/2", (1) 1/2"-3/4", (4) NM
- K.O.s bottom: (1) 1/2"
- Bracket: Horizontal wood spike
- Std. Pkg: 25



Item: 52151-BR

\$3.69 Each

1/2" & 3/4" K.O.S 1-1/2" DEEP

- K.O.s sides: (4) 1/2", (5) 1/2"-3/4"
- K.O.s bottom: (3) 1/2", (2) 1/2"-3/4"
- Bracket: Metal stud
- Std. Pkg: 25




Item: 52151-MS

\$2.49 Each

MC/BX CABLE CLAMPS 1-1/2" DEEP

- K.O.s sides: (2) 1/2", (1) 1/2"-3/4", (4) BX/MC
- K.O.s bottom: (1) 1/2"
- Bracket: Metal stud
- Std. Pkg: 25




Item: 52151-MSBX

\$2.99 Each

NM CABLE CLAMPS 1-1/2" DEEP

- K.O.s sides: (2) 1/2", (1) 1/2"-3/4", (4) NM
- K.O.s bottom: (1) 1/2"
- Bracket: Metal stud
- Std. Pkg: 25



Item: 52151-MSR

\$4.79 Each

1/2" & 3/4" K.O.S 1-1/2" DEEP

- K.O.s sides: (6) 1/2", (3) 1/2"-3/4"
- K.O.s bottom: (3) 1/2", (2) 3/4"
- Bracket: Vertical offset
- Std. Pkg: 25



Item: 52151-DWS

\$1.99 Each

**1/2" K.O.S
1-1/2" DEEP**

- K.O.s sides: (9) 1/2"
- K.O.s bottom: (2) 1/2", (2) 3/4"
- Bracket: Vertical wood spike
- Std. Pkg: 25



Item: 52151-WB

\$1.69 Each

**1/2" & 3/4" K.O.S
1-1/2" DEEP**

- K.O.s sides: (4) 1/2", (5) 1/2"-3/4"
- K.O.s bottom: (3) 1/2", (2) 1/2"-3/4"
- Bracket: Vertical wood spike
- Std. Pkg: 25



Item: 52151-SWB

\$1.79 Each

**MC/BX CABLE
CLAMPS**

1-1/2" DEEP

- K.O.s sides: (2) 1/2", (1) 1/2"-3/4", (4) BX/MC
- K.O.s bottom: (1) 1/2"
- Bracket: Vertical wood spike
- Std. Pkg: 25



Item: 52151-WBBX

\$2.59 Each

**NM CABLE CLAMPS
1-1/2" DEEP**

- K.O.s sides: (2) 1/2", (1) 1/2"-3/4", (4) NM
- K.O.s bottom: (1) 1/2"
- Bracket: Vertical wood spike
- Std. Pkg: 25



Item: 52151-WBR

\$4.99 Each

NEED A CUSTOM BOX FAST!

CALL 847-455-0188

4" SQUARE

1-1/2" Deep Extension Rings

BLANK, NO K.O.S EXTENSION RING 1-1/2" DEEP

- Blank sides
- CALL FOR CUSTOM HOLE PLACEMENT!
- Std. Pkg: 50



Item: 53151-BLNK **\$6.99** Each

1/2" K.O.S EXTENSION RING 1-1/2" DEEP

- K.O.s sides: (12) 1/2"
- Std. Pkg: 50



Item: 53151-1/2 **\$1.59** Each

3/4" K.O.S EXTENSION RING 1-1/2" DEEP

- K.O.s sides: (8) 3/4"
- Std. Pkg: 50



Item: 53151-3/4 **\$2.29** Each

3/4" K.O.S EXTENSION RING 1-1/2" DEEP

- K.O.s sides: (8) 3/4"
- Std. Pkg: 50



Item: 53151-3/4RED **\$3.59** Each

1/2" & 3/4" K.O.S EXTENSION RING 1-1/2" DEEP

- K.O.s sides: (6) 1/2", (6) 1/2"-3/4"
- Std. Pkg: 50



Item: 53151-S **\$1.79** Each

1/2" & 3/4" K.O.S EXTENSION RING 1-1/2" DEEP

- K.O.s sides: (6) 1/2", (6) 1/2"-3/4"
- Std. Pkg: 50



Item: 53151-RED **\$3.29** Each

1/2" & 3/4" AIR-TIGHT K.O.S EXTENSION RING 1-1/2" DEEP

- Extension ring
- K.O.s sides: (8) 1/2", (4) 3/4"
- Std. Pkg: 50



Item: 53151-SVT **\$5.99** Each

STAINLESS STEEL 1/2" & 3/4" AIR-TIGHT K.O.S EXTENSION RING 1-1/2" DEEP

- K.O.s sides: (8) 1/2", (4) 3/4"
- Std. Pkg: 50



Item: 53151-SVTSS **\$39.99** Each

**CONVERTS ONE-GANG TO 4" SQUARE
1/2" & 3/4" K.O.S
1-1/2" DEEP**

- K.O.s sides: (6) 1/2", (6) 1/2"-3/4"
- Fits: One- & two-gang rings & switch boxes
- Std. Pkg: 50



Item: 53151-SUB

\$3.99 Each

**4" SQUARE
BOX EXTENDER**

- Raises box to finished surface
- Std. Pkg: 25




ITEM	ACTUAL RAISED DIMENSION	PRICE EACH
BEX-450	0.56"	\$3.99
BEX-475	0.81"	\$4.39



Need A Special Part Made?

WE CUSTOMIZE

Boxes & Covers | Fittings | Hangers & Clamps



Fast Solutions... Designed By You!

4" SQUARE

2-1/8" Deep Boxes

BLANK, NO K.O.S 2-1/8" DEEP

- Blank sides & bottom
- CALL FOR CUSTOM HOLE PLACEMENT!
- Std. Pkg: 25



Item: 52171-BLNK

\$6.99 Each

STAINLESS STEEL BLANK, NO K.O.S

2-1/8" DEEP

- Blank sides & bottom
- CALL FOR CUSTOM HOLE PLACEMENT!
- Std. Pkg: 25



Item: 52171-BLNKSS

\$39.99 Each

1/2" & 3/4" K.O.S RAISED FOR STEEL WALLS 2-1/8" DEEP

- K.O.s elevated on two sides
- K.O.s sides: (8) 1/2", (4) 1/2"-3/4"
- K.O.s bottom: (2) 1/2", (2) 3/4"
- Std. Pkg: 25



Item: 52171-KOR

\$4.29 Each

1/2" K.O.S 2-1/8" DEEP

- K.O.s sides: (12) 1/2"
- K.O.s bottom: (4) 1/2"
- Std. Pkg: 25



Item: 52171-1/2



\$1.59 Each

1/2" K.O.S DRAWN CONSTRUCTION 2-1/8" DEEP

- K.O.s sides: (12) 1/2"
- K.O.s bottom: (4) 1/2"
- Std. Pkg: 25



Item: 52171-1/2DR



\$2.59 Each

CALL FOR VOLUME DISCOUNTS!

847-455-0188

4" SQUARE
2-1/8" Deep Boxes

3/4" K.O.S
2-1/8" DEEP

- K.O.s sides: (8) 3/4"
- K.O.s bottom: (2) 1/2", (2) 3/4"
- Std. Pkg: 25



Item: 52171-3/4 **\$1.69** Each

3/4" K.O.S
DRAWN CONSTRUCTION
2-1/8" DEEP

- K.O.s sides: (8) 3/4"
- K.O.s bottom: (2) 1/2", (2) 3/4"
- Std. Pkg: 25



Item: 52171-3/4DR **\$2.59** Each

3/4" AIR-TIGHT K.O.S
2-1/8" DEEP

- K.O.s sides: (8) 3/4"
- K.O.s bottom: (3) 1/2", (2) 3/4"
- Patented air-tight nail holes in bottom
- Std. Pkg: 25



Item: 52171-3/4-VT **\$5.99** Each

3/4" K.O.S
2-1/8" DEEP

- K.O.s sides: (8) 3/4"
- K.O.s bottom: (2) 1/2", (2) 3/4"
- Std. Pkg: 25



Item: 52171-3/4RED **\$3.99** Each

1/2" & 3/4" K.O.S
2-1/8" DEEP

- K.O.s sides: (6) 1/2", (6) 1/2"-3/4"
- K.O.s bottom: (1) 1/2", (1) 3/4", (2) 1/2"-3/4"
- Std. Pkg: 50



Item: 52171-S **\$1.39** Each

1/2" & 3/4" K.O.S
GROUND TAIL
2-1/8" DEEP

- Pre-installed 8" ground wire (12 ga) & 10-32 ground screw
- K.O.s sides: (6) 1/2", (6) 1/2"-3/4"
- K.O.s bottom: (1) 1/2", (1) 3/4", (2) 1/2"-3/4"
- Std. Pkg: 25



Item: 52171-SPT **\$2.99** Each

1/2" & 3/4" K.O.S
2-1/8" DEEP

- K.O.s sides: (6) 1/2", (6) 1/2"-3/4"
- K.O.s bottom: (2) 1/2", (2) 3/4"
- Std. Pkg: 25



Item: 52171-SDR **\$2.29** Each

1/2" & 3/4" K.O.S
2-1/8" DEEP

- K.O.s sides: (6) 1/2", (6) 1/2"-3/4"
- K.O.s bottom: (2) 1/2", (2) 3/4"
- Std. Pkg: 25



Item: 52171-RED **\$2.99** Each

4" SQUARE

2-1/8" Deep Boxes

1/2" & 3/4" AIR-TIGHT K.O.S 2-1/8" DEEP

- K.O.s sides: (8) 1/2", (4) 3/4"
- K.O.s bottom: (3) 1/2", (2) 3/4"
- Patented air-tight nail holes in bottom
- Std. Pkg: 25



Item: 52171-SVT **\$4.99** Each

STAINLESS STEEL 1/2" & 3/4" VAPOR-TIGHT K.O.S 2-1/8" DEEP

- K.O.s sides: (8) 1/2", (4) 3/4"
- K.O.s bottom: (3) 1/2", (2) 3/4"
- Std. Pkg: 25



Item: 52171-SVTSS **\$39.99** Each

1/2" & 3/4" AIR-TIGHT K.O.S 2-1/8" DEEP

- K.O.s sides: (8) 1/2", (4) 3/4"
- K.O.s bottom: (3) 1/2", (2) 3/4"
- Patented air-tight nail holes in bottom
- Std. Pkg: 25



Item: 52171-SVTRED **\$6.99** Each

BLANK BOTTOM AIR-TIGHT K.O.S 2-1/8" DEEP

- K.O.s sides: (8) 1/2", (4) 3/4"
- Blank bottom
- Std. Pkg: 25



Item: 52171-SBB **\$6.99** Each

1/2" & 3/4" K.O.S 2-1/8" DEEP

- K.O.s sides: (4) 1", (4) 3/4"
- K.O.s bottom: (2) 1/2", (2) 3/4"
- Std. Pkg: 25



Item: 52171-3/4-1 **\$2.99** Each

3/4" & 1" AIR-TIGHT K.O.S 2-1/8" DEEP

- K.O.s sides: (4) 1", (4) 3/4"
- K.O.s bottom: (2) 1/2", (2) 3/4"
- Patented air-tight nail holes in bottom
- Std. Pkg: 25



Item: 52171-3/4-1VT **\$5.99** Each

1" K.O.S 2-1/8" DEEP

- K.O.s sides: (8) 1"
- K.O.s bottom: (2) 1/2", (2) 3/4"
- Std. Pkg: 25



Item: 52171-1 **\$2.59** Each

1" K.O.S 2-1/8" DEEP

- K.O.s sides: (8) 1"
- K.O.s bottom: (2) 1/2", (2) 3/4"
- Std. Pkg: 25



Item: 52171-1DR **\$3.39** Each

1" AIR-TIGHT K.O.S
2-1/8" DEEP

- K.O.s sides: (8) 1"
- K.O.s bottom: (3) 1/2", (2) 3/4"
- Patented air-tight nail holes in bottom
- Std. Pkg: 25



Item: 52171-1-VT

\$7.99 Each

1" K.O.S
2-1/8" DEEP

- K.O.s sides: (8) 1"
- K.O.s bottom: (2) 1/2", (2) 3/4"
- Std. Pkg: 25



Item: 52171-1-RED

\$3.99 Each

1/2" & 3/4" K.O.S
CUT-IN BOX
2-1/8" DEEP

- K.O.s sides: (6) 1/2", (6) 1/2"-3/4"
- K.O.s bottom: (2) 1/2", (2) 3/4"
- Std. Pkg: 25



Item: 52171-OW

\$4.99 Each

1/2" & 3/4" K.O.S
CUT-IN BOX
2-1/8" DEEP

- K.O.s sides: (6) 1/2", (6) 1/2"-3/4"
- K.O.s bottom: (2) 1/2", (2) 3/4"
- Std. Pkg: 25



Item: 52171-OWRED

\$5.69 Each

MC/BX CABLE
CLAMPS
2-1/8" DEEP

- K.O.s sides: (6) 1/2", (4) MC/BX
- K.O.s bottom: (1) 1/2"
- Std. Pkg: 25



Item: 52171-BX

\$3.69 Each

MC/BX CABLE
CLAMPS
CUT-IN BOX
2-1/8" DEEP

- K.O.s sides: (6) 1/2", (4) MC/BX
- K.O.s bottom: (1) 1/2"
- Std. Pkg: 25



Item: 52171-OWBX

\$4.99 Each

NM CABLE CLAMPS
2-1/8" DEEP

- K.O.s sides: (6) 1/2", (4) NM
- K.O.s bottom: (1) 1/2"
- Std. Pkg: 25



Item: 52171-R

\$3.49 Each

NM CABLE CLAMPS
CUT-IN BOX
2-1/8" DEEP

- K.O.s sides: (6) 1/2", (4) NM
- K.O.s bottom: (1) 1/2"
- Std. Pkg: 25



Item: 52171-OWR

\$4.99 Each

4" SQUARE

2-1/8" Deep Bracket Boxes

1/2" & 3/4" K.O.S 2-1/8" DEEP

- K.O.s sides: (4) 1/2", (5) 1/2"-3/4"
- K.O.s bottom: (3) 1/2", (2) 3/4"-3/4"
- Bracket: Vertical right-angle
- Std. Pkg: 25



Item: 52171-AB

\$3.49 Each

3/4" K.O.S 2-1/8" DEEP

- K.O.s sides: (6) 3/4"
- K.O.s bottom: (3) 1/2", (2) 3/4"
- Bracket: Vertical right-angle
- Std. Pkg: 25



Item: 52171-3/4AB

\$3.69 Each

MC/BX CABLE CLAMPS

2-1/8" DEEP

- K.O.s sides: (4) MC/BX, (3) 1/2"
- K.O.s bottom: (1) 1/2"
- Bracket: Vertical right-angle
- Std. Pkg: 25



Item: 52171-ABBX

\$4.39 Each

NM CABLE CLAMPS

2-1/8" DEEP

- K.O.s sides: (4) NM, (3) 1/2"
- K.O.s bottom: (1) 1/2"
- Bracket: Vertical right-angle
- Std. Pkg: 25



Item: 52171-ABR

\$4.39 Each

1/2" K.O.S 2-1/8" DEEP

- K.O.s sides: (9) 1/2"
- K.O.s bottom: (5) 1/2"
- Bracket: Flat vertical
- Std. Pkg: 25



Item: 52171-F

\$2.29 Each

3/4" K.O.S 2-1/8" DEEP

- K.O.s sides: (6) 3/4"
- K.O.s bottom: (3) 1/2", (2) 3/4"
- Bracket: Flat vertical
- Std. Pkg: 25



Item: 52171-3/4F

\$2.99 Each

1/2" & 3/4" K.O.S 2-1/8" DEEP

- K.O.s sides: (6) 1/2", (3) 1/2"-3/4"
- K.O.s bottom: (3) 1/2", (2) 1/2"-3/4"
- Bracket: Flat vertical
- Std. Pkg: 25



Item: 52171-FS

\$1.99 Each

1/2" & 3/4" K.O.S BRACKET BOX 2-1/8" DEEP

- K.O.s sides: (4) 1/2", (5) 1/2"-3/4"
- K.O.s bottom: (3) 1/2", (2) 1/2"-3/4"
- Std. Pkg: 25



Item: 52171-FRED

\$4.99 Each

4" SQUARE

2-1/8" Deep

MC/BX CABLE CLAMPS

2-1/8" DEEP

- K.O.s sides: (2) 1/2", (1) 1/2"-3/4", (4) MC/BX
- K.O.s bottom: (1) 1/2"
- Bracket: Flat vertical
- Std. Pkg: 25



Item: 52171-FBX

\$3.99 Each

NM CABLE CLAMPS

2-1/8" DEEP

- K.O.s sides: (3) 1/2", (4) NM
- K.O.s bottom: (1) 1/2"
- Bracket: Flat vertical
- Std. Pkg: 25



Item: 52171-FR

\$3.99 Each

1/2" & 3/4" K.O.S

2-1/8" DEEP

- K.O.s sides: (4) 1/2", (5) 1/2"-3/4"
- K.O.s bottom: (3) 1/2", (2) 3/4"
- Bracket: Metal stud
- Std. Pkg: 25




Item: 52171-MS

\$3.49 Each

MC/BX CABLE CLAMPS

2-1/8" DEEP

- K.O.s sides: (2) 1/2", (1) 1/2"-3/4", (4) MC/BX
- K.O.s bottom: (1) 1/2"
- Bracket: Metal stud
- Std. Pkg: 25




Item: 52171-MSBX

\$3.69 Each

NM CABLE CLAMPS

2-1/8" DEEP

- K.O.s sides: (3) 1/2", (4) NM
- K.O.s bottom: (1) 1/2"
- Bracket: Metal stud
- Std. Pkg: 25



Item: 52171-MSR

\$2.99 Each

1/2" K.O.S

2-1/8" DEEP

- K.O.s sides: (9) 1/2"
- K.O.s bottom: (3) 1/2", (2) 1/2"-3/4"
- Bracket: Vertical wood spike
- Std. Pkg: 25



Item: 52171-WB

\$2.49 Each

1/2" & 3/4" K.O.S

2-1/8" DEEP

- K.O.s sides: (4) 1/2", (5) 1/2"-3/4"
- K.O.s bottom: (3) 1/2", (2) 3/4"
- Bracket: Vertical wood spike
- Std. Pkg: 25



Item: 52171-SWB

\$2.49 Each

MC/BX CABLE CLAMPS

2-1/8" DEEP

- K.O.s sides: (2) 1/2", (1) 1/2"-3/4", (4) MC/BX
- K.O.s bottom: (1) 1/2"
- Bracket: Vertical wood spike
- Std. Pkg: 25



Item: 52171-WBBX

\$3.99 Each


CONDUIT BOXES

4" SQUARE

2-1/8" Deep Extension Rings

NM CABLE CLAMPS 2-1/8" DEEP

- K.O.s sides: (3) 1/2", (4) NM
- K.O.s bottom: (1) 1/2"
- Bracket: Vertical wood spike
- Std. Pkg: 25




Item: 52171-WBR

\$3.99 Each

BLANK, NO K.O.S EXTENSION RING 2-1/8" DEEP

- Blank sides
- CALL FOR CUSTOM HOLE PLACEMENT!
- Std. Pkg: 25



Item: 53171-BLNK

\$8.99 Each

1/2" & 3/4" K.O.S ONE-GANG CONVERTER 2-1/8" DEEP

- K.O.s sides: (6) 1/2", (6) 1/2"-3/4"
- Fits: One- & two-gang rings & switch boxes
- Std. Pkg: 25



Item: 53171-SUB

\$6.99 Each

1/2" & 3/4" K.O.S EXTENSION RING 2-1/8" DEEP

- K.O.s sides: (6) 1/2", (6) 1/2"-3/4"
- Std. Pkg: 25



Item: 53171-S

\$3.79 Each

1/2" & 3/4" K.O.S EXTENSION RING 2-1/8" DEEP

- K.O.s sides: (6) 1/2", (6) 1/2"-3/4"
- Std. Pkg: 25



Item: 53171-RED

\$4.99 Each

1/2" & 3/4" AIR-TIGHT K.O.S EXTENSION RING 2-1/8" DEEP

- K.O.s sides: (8) 1/2", (4) 3/4"
- Std. Pkg: 25



Item: 53171-SVT

\$7.99 Each

STAINLESS STEEL 1/2" & 3/4" VAPOR-TIGHT K.O.S EXTENSION RING 2-1/8" DEEP

- K.O.s sides: (8) 1/2", (4) 3/4"
- Std. Pkg: 25



Item: 53171-SVTSS

\$39.99 Each

**3/4" K.O.S
EXTENSION RING
2-1/8" DEEP**

- K.O.s sides: (8) 3/4"
- Std. Pkg: 25



Item: 53171-3/4

\$7.99 Each

**1" K.O.S
EXTENSION RING
2-1/8" DEEP**

- K.O.s sides: (8) 1"
- Std. Pkg: 25



Item: 53171-1

\$7.99 Each

**4" SQUARE ANGLED
EXTENSION RING**

- Angle pitch: 45°
- Slope: From 0.875" rise to 2.85" rise
- Std. Pkg: 10



Item: 53171-A45

\$6.99 Each

**BLANK, NO K.O.S
3-1/2" DEEP**

- Blank sides & bottom
- CALL FOR CUSTOM HOLE PLACEMENT!
- Std. Pkg: 10



Item: 52181-BLNK

\$9.99 Each

**3/4" K.O.S
3-1/2" DEEP**

- K.O.s sides: (8) 3/4"
- K.O.s bottom: (2) 1/2", (2) 3/4"
- Std. Pkg: 25



Item: 52181-3/4

\$6.99 Each

**1" K.O.S
3-1/2" DEEP**

- K.O.s sides: (8) 1"
- K.O.s bottom: (2) 1/2", (2) 3/4"
- Std. Pkg: 25



Item: 52181-3/4-1

\$6.99 Each

**3/4" K.O.S
CONCRETE-SLAB BOX
3-1/2" DEEP**

- K.O.s sides: (8) 3/4"
- K.O.s bottom: Raised ground & concrete-tight K.O.s
- Std. Pkg: 10



Item: 52181-SPKRR

\$7.99 Each

**1/2", 3/4" K.O.S
CONCRETE-SLAB BOX
3-1/2" DEEP**

- K.O.s sides: (4) 1/2", (4) 3/4"
- K.O.s bottom: Raised ground
- Std. Pkg: 10



Item: 52181-SPKR

\$6.99 Each

4" SQUARE

3-1/2" Deep Boxes

1/2" K.O.S CONCRETE-SLAB BOX 3-1/2" DEEP

- K.O.s sides: (8) 1/2"
- K.O.s bottom: Raised ground & concrete-tight K.O.s
- Std. Pkg: 10



Item: 52181-1/2-SPKR \$6.99 Each

3/4" K.O.S CONCRETE-SLAB BOX 3-1/2" DEEP

- K.O.s sides: (8) 3/4"
- K.O.s bottom: Raised ground & concrete-tight K.O.s
- Std. Pkg: 10



Item: 52181-3/4-SPKR \$6.99 Each

1" K.O.S CONCRETE-SLAB BOX 3-1/2" DEEP

- K.O.s sides: (8) 1"
- K.O.s bottom: Raised ground & concrete-tight K.O.s
- Std. Pkg: 10



Item: 52181-1-SPKR \$6.99 Each

3/4" K.O.S 3-1/2" DEEP

- K.O.s sides: (8) 3/4"
- K.O.s bottom: Raised ground & concrete-tight K.O.s
- Std. Pkg: 10



Item: 52181-3/4-SPKRR \$7.99 Each

1/2" & 3/4" & 1" K.O.S 3-1/2" DEEP


- K.O.s sides: (4) 1/2"-3/4", (2) 3/4", (2) 1"
- K.O.s bottom: (2) 1/2", (2) 3/4"
- Std. Pkg: 25



Item: 52181-S \$5.99 Each

1/2" & 3/4" AIR-TIGHT K.O.S 3" DEEP

- K.O.s sides: (8) 1/2", (4) 3/4"
- K.O.s bottom: (3) 1/2", (2) 3/4"
- Patented air-tight nail holes in bottom
- Std. Pkg: 25



Item: 52181-SVT \$9.99 Each

1/2" & 3/4" K.O.S 3-1/2" DEEP

- K.O.s sides: (4) 1/2"-3/4", (2) 3/4", (2) 1"
- K.O.s bottom: (2) 1/2", (2) 3/4"
- Std. Pkg: 10



Item: 52181-RED \$5.99 Each

1/2" & 3/4" K.O.S RIGHT-ANGLE BOX 3-1/2" DEEP



- Extra wiring space & knockouts
- K.O.s: (14) 1/2" & 3/4" concentric
- Raised ground hump
- Std. Pkg: 10



Item: 52181-L \$6.99 Each

4" SQUARE BOX ASSEMBLY WITH ADJUSTABLE 24" T-BAR HANGERS FOR DROP CEILINGS

- Box depth: 3-1/2"
- K.O.s sides: (4) 1/2", (2) 3/4"
- K.O.s bottom: (3) 1/2", (2) 3/4"
- Std. Pkg: 10



Item: 52181-VTBAR

\$11.99 Each



1/2" & 3/4" K.O.S CUT-IN BOX 3-1/2" DEEP

- K.O.s sides: (8) 1/2", (4) 1/2"-3/4"
- K.O.s bottom: (3) 1/2", (2) 1/2"-3/4"
- Std. Pkg: 10



Item: 52181-OW

\$5.99 Each

1/2" & 3/4" K.O.S CUT-IN BOX 3-1/2" DEEP

- K.O.s sides: (8) 1/2", (4) 1/2"-3/4"
- K.O.s bottom: (3) 1/2", (2) 1/2"-3/4"
- Color: Red
- Std. Pkg: 10



Item: 52181-OWRED

\$6.99 Each

1/2" & 3/4" K.O.S 3-1/2" DEEP

- K.O.s sides: (8) 1"
- K.O.s bottom: (2) 1/2", (2) 3/4"
- Std. Pkg: 10




Item: 52181-1

\$6.99 Each

1/2" & 3/4" & 1" K.O.S 3-1/2" DEEP

- K.O.s sides: (4) 1/2"-3/4", (2) 3/4", (2) 1"
- K.O.s bottom: (2) 1/2", (2) 3/4"
- Bracket: Vertical right-angle
- Std. Pkg: 10



Item: 52181-AB

\$5.99 Each

1/2", 3/4" & COMBO K.O.S 3-1/2" DEEP

- K.O.s sides: (5) 1/2", (5) 1/2"-3/4"
- K.O.s bottom: (2) 1/2", (2) 3/4"
- Bracket: Flat vertical 3/4" setback
- Std. Pkg: 10



Item: 52181-FS

\$5.99 Each

1/2" & 3/4" K.O.S BRACKET BOX 3-1/2" DEEP

- K.O.s sides: (5) 1/2", (5) 1/2"-3/4"
- K.O.s bottom: (2) 1/2", (2) 3/4"
- Std. Pkg: 10



Item: 52181-FRED

\$7.59 Each

4" SQUARE

4" Deep Boxes - All

1/2" & 3/4" K.O.S CUT-IN BOX 4" DEEP

- K.O.s sides: (6) 1/2", (6) 1/2"-3/4"
- K.O.s bottom: (2) 1/2", (2) 3/4"
- Std. Pkg: 10



Item: 52191-OWRED **\$8.59** Each

1" K.O.S 4" DEEP

- K.O.s sides: (8) 1"
- K.O.s bottom: (2) 1/2", (2) 3/4"
- Std. Pkg: 10



Item: 52191-1 **\$8.99** Each

BLANK, NO K.O.S 4" DEEP

- Blank sides & bottom
- CALL FOR CUSTOM HOLE PLACEMENT!
- Std. Pkg: 10



Item: 52191-BLNK **\$11.99** Each

3/4" K.O.S 4" DEEP

- K.O.s sides: (8) 3/4"
- K.O.s bottom: (2) 1/2", (2) 3/4"
- Std. Pkg: 10



Item: 52191-3/4 **\$8.99** Each

1/2", 3/4" & 1" K.O.S 4" DEEP

- K.O.s sides: (4) 1/2"-3/4", (2) 3/4", (2) 1"
- K.O.s bottom: (2) 1/2", (2) 3/4"
- Std. Pkg: 10



Item: 52191-S **\$7.99** Each

1/2", 3/4" & 1" K.O.S 4" DEEP

- K.O.s sides: (4) 1/2"-3/4", (2) 3/4", (2) 1"
- K.O.s bottom: (2) 1/2", (2) 3/4"
- Std. Pkg: 10



Item: 52191-RED **\$7.99** Each

1/2" & 3/4" K.O.S CUT-IN BOX 4" DEEP

- K.O.s sides: (6) 1/2", (6) 1/2"-3/4"
- K.O.s bottom: (2) 1/2", (2) 3/4"
- Std. Pkg: 10



Item: 52191-OW **\$7.99** Each

1/2" & 3/4" K.O.S BRACKET BOX 4" DEEP

- K.O.s sides: (5) 1/2", (5) 1/2"-3/4"
- K.O.s bottom: (2) 1/2", (2) 3/4"
- Bracket: Flat vertical
- Std. Pkg: 10



Item: 52191-FRED **\$8.99** Each

1/2" & 3/4" K.O.S
1-1/2" DEEP

- K.O.s sides: (8) 1/2", (4) 1/2"-3/4"
- K.O.s bottom: (2) 1/2", (2) 3/4"
- Std. Pkg: 25



Item: 72151-S

\$3.79 Each

3/4" K.O.S
1-1/2" DEEP

- K.O.s sides: (12) 3/4"
- K.O.s bottom: (3) 1/2", (2) 3/4"
- Std. Pkg: 25



Item: 72151-3/4

\$5.99 Each

1/2" & 3/4" K.O.S
1-1/2" DEEP

- K.O.s sides: (8) 1/2", (4) 3/4"
- K.O.s bottom: (3) 1/2", (2) 3/4"
- Std. Pkg: 25




Item: 72151-SVT

\$6.99 Each

1/2" K.O.S
1-1/2" DEEP

- K.O.s sides: (6) 1/2", (6) 1/2"-3/4"
- Drawn, solid construction
- Std. Pkg: 25



Item: 73151-S

\$5.99 Each

4-11/16" SQUARE

2-1/8" Deep Boxes

RED FIRE ALARM DEVICE BOX 2-1/8" DEEP



ITEM	K.O.S SIDES	K.O.S BOTTOM	STD. PKG.	PRICE EACH
82171-RD	(10) 1/2" & 3/4", (2) 1"	(3) 1/2", (2) 3/4"	25	\$5.99

**Perfect Device Fit
NO OVERHANG**



Old, ugly install.



New...Perfect Fit!

WHITE FIRE ALARM DEVICE BOX 2-1/8" DEEP



ITEM	K.O.S SIDES	K.O.S BOTTOM	STD. PKG.	PRICE EACH
82171-WH	(10) 1/2" & 3/4", (2) 1"	(3) 1/2", (2) 3/4"	25	\$5.99

**Perfect Device Fit
NO OVERHANG**



Old, ugly install.



New...Perfect Fit!

4-11/16" SQUARE

2-1/8" Deep Boxes

BLANK, NO K.O.S 2-1/8" DEEP

- Blank sides & bottom
- Drawn, solid construction
- Std. Pkg: 25



Item: 72171-BLNK

\$8.99 Each

BLANK, NO K.O.S 2-1/8" DEEP

- Blank sides & bottom
- Welded construction
- Std. Pkg: 25



Item: 72171-BLNKW

\$8.99 Each

BLANK, NO K.O.S STAINLESS STEEL 2-1/8" DEEP

- 316 Stainless steel
- Blank sides & bottom
- Std. Pkg: 25



Item: 72171-BLNKSS

\$39.99 Each

1/2" K.O.S 2-1/8" DEEP

- K.O.s sides: (12) 1/2"
- K.O.s bottom: (2) 1/2", (2) 3/4"
- Std. Pkg: 25



Item: 72171-1/2

\$4.99 Each

1/2" K.O.S 2-1/8" DEEP

- K.O.s sides: (12) 1/2"
- K.O.s bottom: (2) 1/2", (2) 3/4"
- Welded construction
- Std. Pkg: 25



Item: 72171-1/2W

\$4.99 Each

3/4" K.O.S 2-1/8" DEEP

- K.O.s sides: (12) 3/4"
- K.O.s bottom: (2) 1/2", (2) 3/4"
- Std. Pkg: 25



Item: 72171-3/4

\$3.49 Each

3/4" K.O.S 2-1/8" DEEP

- K.O.s sides: (12) 3/4"
- K.O.s bottom: (2) 1/2", (2) 3/4"
- Std. Pkg: 25



Item: 72171-3/4W

\$3.59 Each

3/4" K.O.S 2-1/8" DEEP

- K.O.s sides: (12) 3/4"
- K.O.s bottom: (2) 1/2", (2) 3/4"
- Std. Pkg: 25



Item: 72171-3/4RED

\$6.79 Each

4-11/16" SQUARE

2-1/8" Deep Boxes

1/2" & 3/4" AIR-TIGHT K.O.S 2-1/8" DEEP

- K.O.s sides: (12) 3/4"
- K.O.s bottom: (3) 1/2", (2) 3/4"
- Std. Pkg: 25



Item: 72171-3/4-VT **\$6.99** Each

1/2" & 3/4" K.O.S 2-1/8" DEEP

- K.O.s sides: (6) 1/2", (6) 1/2"-3/4"
- K.O.s bottom: (2) 1/2", (2) 3/4"
- Std. Pkg: 25



Item: 72171-S **\$3.49** Each

1/2" & 3/4" K.O.S 2-1/8" DEEP

- K.O.s sides: (6) 1/2", (6) 1/2"-3/4"
- K.O.s bottom: (2) 1/2", (2) 3/4"
- Std. Pkg: 25



Item: 72171-SW **\$3.29** Each

1/2" & 3/4" K.O.S 2-1/8" DEEP

- K.O.s sides: (6) 1/2", (6) 1/2"-3/4"
- K.O.s bottom: (2) 1/2", (2) 3/4"
- Painted red
- Std. Pkg: 25



Item: 72171-RED **\$3.99** Each

1/2" & 3/4" AIR-TIGHT K.O.S 2-1/8" DEEP

- K.O.s sides: (8) 1/2", (4) 3/4"
- K.O.s bottom: (3) 1/2", (2) 3/4"
- Std. Pkg: 25



Item: 72171-SVT **\$6.99** Each

1/2" & 3/4" AIR-TIGHT K.O.S 2-1/8" DEEP

- K.O.s sides: (8) 1/2", (4) 3/4"
- K.O.s bottom: (3) 1/2", (2) 3/4"
- Painted red
- Std. Pkg: 25



Item: 72171-SVTRED **\$7.99** Each

STAINLESS STEEL 1/2" & 3/4" AIR-TIGHT K.O.S 2-1/8" DEEP

- K.O.s sides: (8) 1/2", (4) 3/4"
- K.O.s bottom: (3) 1/2", (2) 3/4"
- 316 Stainless steel
- Std. Pkg: 25



Item: 72171-SVTSS **\$39.99** Each

3/4" & 1" K.O.S 2-1/8" DEEP

- K.O.s sides: (6) 3/4", (4) 1" on opposing sides
- K.O.s bottom: (2) 1/2", (2) 3/4"
- Std. Pkg: 25



Item: 72171-3/4-1 **\$3.99** Each

3/4" & 1" K.O.S
2-1/8" DEEP

- K.O.s sides: (6) 3/4", (4) 1"
- K.O.s bottom: (2) 1/2", (2) 3/4"
- Std. Pkg: 25



Item: 72171-3/4-1W **\$3.99** Each

3/4" & 1" K.O.S
2-1/8" DEEP

- K.O.s sides: (6) 3/4", (4) 1"
- K.O.s bottom: (3) 1/2", (2) 3/4"
- Std. Pkg: 25



Item: 72171-3/4-1VT **\$6.99** Each

1" K.O.S
2-1/8" DEEP

- K.O.s sides: (8) 1"
- K.O.s bottom: (2) 1/2", (2) 3/4"
- Std. Pkg: 25



Item: 72171-1 **\$3.99** Each

1" K.O.S
2-1/8" DEEP

- K.O.s sides: (8) 1"
- K.O.s bottom: (2) 1/2", (2) 3/4"
- Std. Pkg: 25



Item: 72171-1W **\$3.99** Each

1" K.O.S
2-1/8" DEEP

- K.O.s sides: (12) 1"
- K.O.s bottom: (2) 1/2", (2) 3/4"
- Painted red
- Std. Pkg: 25



Item: 72171-1RED **\$6.99** Each

1" AIR-TIGHT K.O.S
2-1/8" DEEP

- K.O.s sides: (8) 1"
- K.O.s bottom: (3) 1/2", (2) 3/4"
- Std. Pkg: 25



Item: 72171-1VT **\$7.99** Each

1" & 1-1/4" K.O.S
2-1/8" DEEP

- K.O.s sides: (4) 1-1/4", (4) 1"
- K.O.s bottom: (2) 1/2", (2) 3/4"
- Std. Pkg: 25



Item: 72171-1-1/4 **\$5.99** Each

1" & 1-1/4" K.O.S
2-1/8" DEEP

- K.O.s sides: (4) 1-1/4", (4) 1"
- K.O.s bottom: (2) 1/2", (2) 3/4"
- Std. Pkg: 25



Item: 72171-1-1/4W **\$5.99** Each

4-11/16" SQUARE

2-1/8" Deep Bracket Boxes

1-1/4" AIR-TIGHT K.O.S 2-1/8" DEEP


- K.O.s sides: (4) 1-1/4"
- K.O.s bottom: (3) 1/2", (2) 3/4"
- Std. Pkg: 25



Item: 72171-1-1/4VT **\$7.99** Each

MC/BX CABLE CLAMPS 2-1/8" DEEP


- K.O.s sides: (6) 1/2"-3/4", (4) MC/BX
- K.O.s bottom: (3) 1/2", (2) 3/4"
- Std. Pkg: 25



Item: 72171-BXW **\$5.99** Each

1/2" & 3/4" K.O.S 2-1/8" DEEP


- K.O.s sides: (2) 1/2", (7) 1/2"-3/4"
- K.O.s bottom: (2) 1/2", (2) 3/4"
- Bracket: Metal stud
- Std. Pkg: 25



Item: 72171-MSW **\$4.79** Each

MC/BX CABLE CLAMPS 2-1/8" DEEP

- K.O.s sides: (3) 1/2"-3/4", (4) MC/BX
- K.O.s bottom: (3) 1/2", (2) 3/4"
- Bracket: Metal stud
- Std. Pkg: 25



Item: 72171-MSBXW **\$6.99** Each

1/2" & 3/4" K.O.S 2-1/8" DEEP


- K.O.s sides: (2) 1/2", (7) 1/2"-3/4"
- K.O.s bottom: (2) 1/2", (2) 3/4"
- Bracket: Flat vertical
- Std. Pkg: 25



Item: 72171-FSW **\$4.29** Each

MC/BX CABLE CLAMPS 2-1/8" DEEP

- K.O.s sides: (6) 1/2"-3/4", (4) MC/BX
- K.O.s bottom: (3) 1/2", (2) 3/4"
- Bracket: Flat vertical
- Std. Pkg: 25



Item: 72171-FBXW **\$5.99** Each

GARVIN
ELECTRICAL MANUFACTURER

Got A Product Idea!

WE CAN MAKE IT



Your Dream Can Become Reality!

BLANK, NO K.O.S
3" DEEP

- Blank sides & bottom
- Welded construction
- Std. Pkg: 25



Item: 72181-BLNK **\$10.99** Each

3/4" K.O.S
3" DEEP

- K.O.s sides: (12) 3/4"
- K.O.s bottom: (2) 1/2"-3/4"
- Std. Pkg: 25



Item: 72181-3/4 **\$6.99** Each



DATA CABLE BOX
3" DEEP

- K.O.s sides: (2) 1/2" & 3/4", (2) 1" & 1-1/4", (2) 1", 1-1/4" & 1-1/2"
- K.O.s bottom: (2) 1/2" & concentric (2) 3/4 & 1"
- 3-screw ground hump
- Std. Pkg: 10



Item: 72181-DTA **\$6.99** Each



1/2" K.O.S
3" DEEP

- K.O.s sides: (2) 1/2", (10) 1/2"-3/4"
- K.O.s bottom: (2) 1/2"-3/4"
- Std. Pkg: 25



Item: 72181-S **\$6.99** Each



1" K.O.S
3" DEEP

- K.O.s sides: (8) 1"
- K.O.s bottom: (2) 1/2", (2) 3/4"
- Std. Pkg: 25



Item: 72181-1 **\$7.99** Each



1-1/4" K.O.S
3" DEEP

- K.O.s sides: (8) 1-1/4"
- K.O.s bottom: (2) 1/2", (2) 3/4"
- Std. Pkg: 25



Item: 72181-1-1/4 **\$8.99** Each



1-1/2" K.O.S
3" DEEP

- K.O.s sides: (4) 1-1/2"
- K.O.s bottom: (2) 1/2", (2) 3/4"
- Std. Pkg: 25



Item: 72181-1-1/2 **\$9.99** Each



DATA CABLE BOX
3" DEEP

- K.O.s sides: All concentric (2) 1/2" & 3/4, (2) 1" & 1-1/4", (2) 1", 1-1/4" & 1-1/2"
- K.O.s bottom: (2) 1/2" & concentric (2) 3/4 & 1"
- 3-screw ground hump & angle bracket
- Std. Pkg: 10



Item: 72181-DTAB **\$8.99** Each



4-11/16" SQUARE

Extension Rings (All Depths)

1/2" K.O.S 1-1/2" DEEP

- K.O.s sides: (6) 1/2", (6) 1/2"-3/4"
- Welded construction
- Std. Pkg: 25



Item: 73151-SW

\$5.99 Each

1/2" K.O.S 1-1/2" DEEP

- K.O.s sides: (6) 1/2", (6) 1/2"-3/4"
- Drawn construction
- Std. Pkg: 25



Item: 73151-S

\$5.99 Each

BLANK, NO K.O.S 2-1/8" DEEP

- Blank sides
- Drawn construction
- Std. Pkg: 25



Item: 73171-BLNK

\$10.99 Each

BLANK, NO K.O.S 2-1/8" DEEP

- Blank sides
- Welded construction
- Std. Pkg: 25



Item: 73171-BLNKW

\$10.99 Each

1/2" K.O.S 2-1/8" DEEP

- K.O.s sides: (12) 1/2"
- Drawn construction
- Std. Pkg: 25



Item: 73171-1/2

\$9.99 Each

3/4" K.O.S 2-1/8" DEEP

- K.O.s sides: (12) 3/4"
- Drawn construction
- Std. Pkg: 25



Item: 73171-3/4

\$9.99 Each

3/4" K.O.S 2-1/8" DEEP

- K.O.s sides: (12) 3/4"
- Welded construction
- Std. Pkg: 25



Item: 73171-3/4W

\$9.99 Each

1/2" & 3/4" K.O.S 2-1/8" DEEP

- K.O.s sides: (6) 1/2", (6) 1/2"-3/4"
- Drawn construction
- Std. Pkg: 25



Item: 73171-S

\$3.99 Each

**1/2" & 3/4" K.O.S
EXTENSION RING
2-1/8" DEEP**

- K.O.s sides: (6) 1/2", (6) 1/2"-3/4"
- Std. Pkg: 25



Item: 73171-SW

\$3.99 Each

**1/2" & 3/4" K.O.S
EXTENSION RING
2-1/8" DEEP**

- K.O.s sides: (6) 1/2", (6) 1/2"-3/4"
- Std. Pkg: 25



Item: 73171-RED

\$8.99 Each

**1/2" & 3/4" AIR-TIGHT K.O.S
EXTENSION RING
2-1/8" DEEP**

- K.O.s sides: (8) 1/2", (4) 3/4"
- Std. Pkg: 25



Item: 73171-SVT

\$8.99 Each

**STAINLESS STEEL
1/2" & 3/4" VAPOR-TIGHT K.O.S
EXTENSION RING
2-1/8" DEEP**

- K.O.s sides: (8) 1/2", (4) 3/4"
- 316 Stainless steel
- Std. Pkg: 25



Item: 73171-SVTSS

\$39.99 Each

**1/2" & 3/4" K.O.S
ONE-GANG CONVERTER
2-1/8" DEEP**

- Mounts on one- & two-gang boxes & device rings
- K.O.s sides: (2) 1/2", (10) 1/2"-3/4"
- Std. Pkg: 25



Item: 73171-SUB

\$9.99 Each

**1" K.O.S
EXTENSION RING
2-1/8" DEEP**

- K.O.s sides: (8) 1"
- Drawn, solid construction
- Std. Pkg: 25



Item: 73171-1

\$9.99 Each

**1" K.O.S
EXTENSION RING
2-1/8" DEEP**

- K.O.s sides: (8) 1"
- Std. Pkg: 25



Item: 73171-1W

\$9.99 Each

**1-1/4" K.O.S
EXTENSION RING
2-1/8" DEEP**

- K.O.s sides: (8) 1-1/4"
- Std. Pkg: 25



Item: 73171-1-1/4W

\$6.99 Each

4-11/16" SQUARE

Extension Rings (All Depths)

BLANK, NO K.O.S EXTENSION RING 3" DEEP

- Blank sides
- Std. Pkg: 25



Item: 73181-BLNK

\$13.99 Each

1/2" & 3/4" K.O.S EXTENSION RING 3" DEEP

- K.O.s sides: (6) 1/2",
(6) 1/2"-3/4"
- Std. Pkg: 25



Item: 73181-SW


\$10.99 Each



Need A Special Part Made?

WE CUSTOMIZE

Boxes & Covers | Fittings | Hangers & Clamps



Fast Solutions... Designed By You!

BLANK, NO K.O.S
2-7/8" DEEP

- Let us custom punch to your specification
- Std. Pkg: 10



Item: 5SQBLNK

\$7.99 Each

1/2" & 3/4" K.O.S
2-7/8" DEEP

- K.O.s sides: (12) 1/2-3/4"
- K.O.s bottom: (2) 3/4", (3) 1/2"
- Std. Pkg: 10



Item: 5SQ5075

\$6.99 Each

1/2", 3/4" & 1" K.O.S
2-7/8" DEEP

- K.O.s sides: (4) 1/2-3/4", (4) 1/2", (4) 1"
- K.O.s bottom: (2) 3/4", (3) 1/2"
- Std. Pkg: 10




Item: 5SQ5075100

\$6.99 Each

1/2" & 3/4" K.O.S
OLD-WORK CUT-IN BOX
2-7/8" DEEP

- K.O.s sides: (2) 1/2", (10) 1/2-3/4"
- K.O.s bottom: (2) 3/4", (3) 1/2"
- Std. Pkg: 10



Item: 5SQ50750W

\$7.99 Each

1/2" & 1" K.O.S
2-7/8" DEEP

- K.O.s sides: (4) 1/2, (8) 1"
- K.O.s bottom: (2) 3/4", (3) 1/2"
- Std. Pkg: 10



Item: 5SQ50100

\$6.99 Each

1" & 1-1/4" K.O.S
2-7/8" DEEP

- K.O.s sides: (4) 1", (4) 1-1/4"
- K.O.s bottom: (2) 3/4", (3) 1/2"
- Std. Pkg: 10



Item: 5SQ100125

\$6.99 Each



5SQ5075100 In-Use


5" SQUARE ASSEMBLIES

3" Deep

1/2" & 3/4" K.O.S WITH HINGED DEVICE-RING MOUNTING PLATE



ITEM	DESCRIPTION	FOR SIDE STANDOFF	STD. PKG.	PRICE EACH
5PF5075	1/2" & 3/4" K.O.s Hinged plate accepts any 4" square cover or device ring	3-1/2"	25	\$6.99



1/2" & 3/4" K.O.S BRACKET BOX WITH HINGED DEVICE-RING MOUNTING PLATE



ITEM	BRACKET	DESCRIPTION	FOR SIDE STANDOFF	STD. PKG.	PRICE EACH
5PF5075AB	AB Vertical Angle	1/2" & 3/4" K.O.s. with angle bracket for stud walls. Hinged plate accepts any 4" square cover or device ring	3-1/2"	25	\$7.99



1/2" & 3/4" K.O.S WITH HINGED BLANK COVER




ITEM	BRACKET	DESCRIPTION	STD. PKG.	PRICE EACH
HP-0000	None	1/2" & 3/4" K.O.s. Flat blank cover on hinged door.	25	\$4.99




**1/2" & 3/4" K.O.S
WITH HINGED ONE-GANG
DEVICE RING**

ITEM	RAISED RING	STD. PKG.	PRICE EACH
HP-100	Flat	25	\$4.99
HP-125	1/4"	25	\$4.99
HP-150	1/2"	50	\$4.99
HP-158	5/8"	50	\$4.99
HP-175	3/4"	25	\$4.99
HP-1100	1"	25	\$4.99
HP-1125	1-1/4"	25	\$4.99
HP-1150	1-1/2"	25	\$4.99
HP-1200	2"	25	\$4.99



OPEN





CONNECT




CLOSE

**1/2" & 3/4" K.O.S
WITH HINGED ONE-GANG
ADJUSTABLE-DEPTH
DEVICE RING**

ITEM	ADJUSTABLE DEPTH	DESCRIPTION	STD. PKG.	PRICE EACH
HP-AMR158	5/8" - 1-1/4"	Device ring adjusts to wall depth. Door opens for quick connect.	25	\$6.99
HP-AMR1	3/4" - 1-1/2"		25	\$6.99



OPEN



CONNECT



CLOSE

5" SQUARE ASSEMBLIES

3" Deep

1/2" & 3/4" K.O.S HINGED ONE-GANG DEVICE RING & ANGLE BRACKET

ITEM	RAISED RING	STD. PKG.	PRICE EACH
HPAB-100	Flat	25	\$6.99
HPAB-125	1/4"	25	\$6.99
HPAB-150	1/2"	25	\$6.99
HPAB-158	5/8"	25	\$6.99
HPAB-175	3/4"	25	\$6.99
HPAB-1100	1"	25	\$6.99
HPAB-1125	1-1/4"	25	\$6.99
HPAB-1150	1-1/2"	25	\$6.99
HPAB-1200	2"	25	\$6.99



OPEN




CONNECT



CLOSE

1/2" & 3/4" K.O.S HINGED ONE-GANG ADJUSTABLE-DEPTH DEVICE RING & ANGLE BRACKET

ITEM	ADJUSTABLE DEPTH	STD. PKG.	PRICE EACH
HPAB-AMR158	5/8" - 1-1/4"	25	\$6.99
HPAB-AMR1	3/4" - 1-1/2"	25	\$6.99



OPEN



CONNECT




CLOSE

**1/2" & 3/4" K.O.S
HINGED TWO-GANG
DEVICE RING**

ITEM	RAISED RING	STD. PKG.	PRICE EACH
HP-200	Flat	25	\$4.99
HP-225	1/4"	25	\$4.99
HP-250	1/2"	25	\$4.99
HP-258	5/8"	25	\$4.99
HP-275	3/4"	25	\$4.99
HP-2100	1"	25	\$4.99
HP-2125	1-1/4"	25	\$4.99
HP-2150	1-1/2"	25	\$4.99
HP-2200	2"	25	\$4.99



OPEN



CONNECT




CLOSE

**1/2" & 3/4" K.O.S
HINGED TWO-GANG
ADJUSTABLE-DEPTH
DEVICE RING**

ITEM	ADJUSTABLE DEPTH	STD. PKG.	PRICE EACH
HP-AMR2	3/4" - 1-1/2"	25	\$6.99



OPEN



CONNECT




CLOSE

**1/2" & 3/4" K.O.S
HINGED TWO-GANG DEVICE
RING & ANGLE BRACKET**

ITEM	RAISED RING	STD. PKG.	PRICE EACH
HPAB-200	Flat	25	\$6.99
HPAB-225	1/4"	25	\$6.99
HPAB-250	1/2"	25	\$6.99
HPAB-258	5/8"	25	\$6.99
HPAB-275	3/4"	25	\$6.99
HPAB-2100	1"	25	\$6.99
HPAB-2125	1-1/4"	25	\$6.99
HPAB-2150	1-1/2"	25	\$6.99
HPAB-2200	2"	25	\$6.99



OPEN



CONNECT





CLOSE

5" SQUARE ASSEMBLIES


3" Deep Box/Cover Assemblies

1/2" & 3/4" K.O.S WITH HINGED TWO-GANG ADJUSTABLE-DEPTH DEVICE RING & ANGLE BRACKET

ITEM	ADJUSTABLE DEPTH	STD. PKG.	PRICE EACH
HPAB-AMR2	3/4" - 1-1/2"	25	\$6.99



OPEN



CONNECT



CLOSE

1/2" & 3/4" K.O.S HINGED INDUSTRIAL COVER



HP1929

ITEM	DEVICE OPENINGS	STD. PKG.	PRICE EACH
HP1929	Blank - No device	10	\$4.99
HP1930	1/2" Knockout	10	\$4.99
HP1932	Single Receptacle 1.406" Diameter	10	\$4.99
HP1934	30-50 Amp 2.10" Diameter	10	\$4.99
HP1935	Toggle	10	\$4.99
HP1938	Duplex	10	\$4.99
HP1942	20 Amp 1.594" Diameter	10	\$4.99
HP1943	30 Amp 1.719" Diameter	10	\$4.99
HP1944	30 Amp 2.141" Diameter	10	\$4.99
HP1947	GFCI/DECOR	10	\$4.99
HP1949	30-60 Amp 2.437" Diameter	10	\$4.99

NOTE: Box & hinged cover only - Devices not included.



HP1930



HP1932



HP1934



HP1935



HP1938



HP1942



HP1943



HP1944



HP1947




HP1949

5" SQUARE ASSEMBLIES

3" Deep Box/Cover Assemblies

1/2" & 3/4" K.O.S WITH HINGED INDUSTRIAL COVER




ITEM	DEVICES	STD. PKG.	PRICE EACH
HP1933	(2) Single Receptacles 1.406" Diameter	10	\$4.99
HP1936	(2) Toggle	10	\$4.99
HP1937	Toggle / Single Receptacle 1.406" Diameter	10	\$4.99
HP1939	(2) Duplex	10	\$4.99
HP1940	Duplex / Single Receptacle 1.406" Diameter	10	\$4.99
HP1941	Toggle / Duplex	10	\$4.99
HP1948	Toggle / GFCI	10	\$4.99
HP1950	(2) GFCI / DECOR	10	\$4.99
HP1951	Duplex / GFCI	10	\$4.99
HP1952	GFCI / Single Receptacle 1.406" Diameter	10	\$4.99

NOTE: Box & hinged cover only - Devices not included.



HP1933



HP1936



HP1937



HP1939



HP1940



HP1941



HP1948



HP1950



HP1951



HP1952

CONDUIT BOXES

6" SQUARE

1-1/2" to 3-1/2" Deep

BLANK, NO K.O.S 1-1/2" DEEP

- Blank sides & bottom
- Std. Pkg: 10



Item: 6150-BLNK

\$9.99 Each

1/2" K.O.S 1-1/2" DEEP

- Side K.O.s: (6) 1/2", (6) 1/2"-3/4"
- Bottom K.O.s: (2) 1/2", (2) 3/4"
- Std. Pkg: 10



Item: 6150-S

\$6.99 Each

BLANK, NO K.O.S 2-1/2" DEEP

- Blank sides & bottom
- Std. Pkg: 10



Item: 6250-BLNK

\$9.99 Each

1/2" K.O.S 2-1/2" DEEP

- Side K.O.s: (6) 1/2", (6) 1/2"-3/4"
- Bottom K.O.s: (2) 1/2", (2) 3/4"
- Std. Pkg: 10



Item: 6250-S

\$6.99 Each

3/4" K.O.S 2-1/2" DEEP

- Side K.O.s: (12) 3/4"
- Bottom K.O.s: (3) 1/2", (2) 3/4"
- Std. Pkg: 10



Item: 6250-3/4

\$6.99 Each

1" K.O.S 2-1/2" DEEP

- Side K.O.s: (12) 1"
- Bottom K.O.s: (3) 1/2", (2) 3/4"
- Std. Pkg: 10



Item: 6250-1

\$6.99 Each

1-1/4" K.O.S 2-1/2" DEEP

- Side K.O.s: (8) 1-1/4"
- Bottom K.O.s: (3) 1/2", (2) 3/4"
- Std. Pkg: 10



Item: 6250-1-1/4

\$6.99 Each

BLANK, NO K.O.S 3-1/2" DEEP

- Blank sides & bottom
- Std. Pkg: 10



Item: 6350-BLNK

\$11.99 Each

6" SQUARE
1-1/2" to 3-1/2" Deep

1/2" K.O.S
3-1/2" DEEP

- Side K.O.s: (6) 1/2", (6) 1/2"-3/4"
- Bottom K.O.s: (2) 1/2", (2) 3/4"
- Std. Pkg: 10



Item: 6350-S

\$7.99 Each

3/4" K.O.S
3-1/2" DEEP

- Side K.O.s: (12) 3/4"
- Bottom K.O.s: (3) 1/2", (2) 3/4"
- Std. Pkg: 10



Item: 6350-3/4

\$7.99 Each

1" K.O.S
3-1/2" DEEP

- Side K.O.s: (12) 1"
- Bottom K.O.s: (3) 1/2", (2) 3/4"
- Std. Pkg: 10



Item: 6350-1

\$7.99 Each

1-1/4" K.O.S
3-1/2" DEEP

- Side K.O.s: (8) 1-1/4"
- Bottom K.O.s: (3) 1/2", (2) 3/4"
- Std. Pkg: 10



Item: 6350-1-1/4

\$8.99 Each

1-1/2" K.O.S
3-1/2" DEEP

- Side K.O.s: (8) 1-1/2"
- Bottom K.O.s: (3) 1/2", (2) 3/4"
- Std. Pkg: 10



Item: 6350-1-1/2

\$8.99 Each

CALL FOR VOLUME DISCOUNTS!

847-455-0188

1/2" & 3/4" K.O.S
EXTENSION RINGS

- Side K.O.s: (6) 1/2", (6) 1/2"-3/4"
- Std. Pkg: 10



ITEM	DEPTH	PRICE EACH
6150-EXT	1-1/2"	\$6.99
6250-EXT	2-1/2"	\$8.99
6350-EXT	3-1/2"	\$9.99

**C
O
N
D
U
I
T

B
O
X
E
S**

HANDY/UTILITY

1-1/2" to 1-7/8" Deep

BLANK, NO K.O.S MINI HANDY BOX 1-1/2" DEEP

- Size: 3-3/4" H x 1-1/2" W
- Blank sides & bottom
- Std. Pkg: 50



Item: **G19180-BLNK**

\$3.49 Each

1/2" K.O.S MINI HANDY BOX 1-1/2" DEEP

- Size: 3-3/4" H x 1-1/2" W
- Side K.O.s: (8) 1/2"
- Bottom K.O.s: (3) 1/2"
- Offset sidewall ears
- Std. Pkg: 50



Item: **G19180**

\$2.89 Each



1/2" K.O.S 1-1/4" DEEP

- Side K.O.s: (8) 1/2"
- Bottom K.O.s: (2) 1/2"
- Ground connection hump
- Std. Pkg: 50



Item: **G19279**

\$1.99 Each



1/2" K.O.S 1-1/2" DEEP

- Side K.O.s: (8) 1/2"
- Bottom K.O.s: (2) 1/2"
- Ground connection hump
- Std. Pkg: 50



Item: **G19280**

\$1.29 Each



BLANK, NO K.O.S 1-7/8" DEEP

- Blank sides & bottom
- Std. Pkg: 50



Item: **G19281-BLNK**

\$4.99 Each

STAINLESS STEEL BLANK, NO K.O.S 1-7/8" DEEP

- Blank sides & bottom
- Std. Pkg: 50



Item: **G19281-BLNKSS**

\$20.99 Each

1/2" K.O.S 1-7/8" DEEP

- Side K.O.s: (8) 1/2"
- Bottom K.O.s: (2) 1/2"
- Ground hump
- Std. Pkg: 50



Item: **G19281**

\$0.89 Each



STAINLESS STEEL 1/2" K.O.S 1-7/8" DEEP

- Side K.O.s: (8) 1/2"
- Bottom K.O.s: (2) 1/2"
- Ground hump
- Std. Pkg: 50



Item: **G19281-SS**

\$19.99 Each



HANDY/UTILITY

1-7/8" to 2-1/2" Deep

1/2" K.O.S 1-7/8" DEEP

- No ground hump (NGH)
- Side K.O.s: (8) 1/2"
- Bottom K.O.s: (3) 1/2"
- Std. Pkg: 50



Item: G19281NGH

\$1.99 Each

3/4" K.O.S 1-7/8" DEEP

- Side K.O.s: (6) 3/4"
- Bottom K.O.s: (1) 3/4"
- Ground connection hump
- Std. Pkg: 50



Item: G19281-3/4

\$1.89 Each

BLANK, NO K.O.S 2-1/8" DEEP

- Blank sides & bottom
- Std. Pkg: 50



Item: G19282-BLNK

\$5.99 Each

STAINLESS STEEL BLANK, NO K.O.S 2-1/8" DEEP

- Blank sides & bottom
- 316 Stainless steel
- Std. Pkg: 50



Item: G19282-BLNKSS

\$23.99 Each

1/2" K.O.S 2-1/8" DEEP

- Side K.O.s: (8) 1/2"
- Bottom K.O.s: (2) 1/2"
- Ground hump
- Std. Pkg: 50



Item: G19282

\$1.59 Each

STAINLESS STEEL 1/2" K.O.S 2-1/8" DEEP

- Side K.O.s: (8) 1/2"
- Bottom K.O.s: (2) 1/2"
- Ground hump
- Std. Pkg: 50



Item: G19282-SS

\$22.99 Each

1/2" K.O.S 2-1/8" DEEP

- No ground hump (NGH)
- Side K.O.s: (8) 1/2"
- Bottom K.O.s: (3) 1/2"
- Std. Pkg: 50



Item: G19282NGH

\$1.99 Each

3/4" K.O.S 2-1/8" DEEP

- Side K.O.s: (6) 3/4"
- Bottom K.O.s: (1) 3/4"
- Ground hump
- Std. Pkg: 50



Item: G19282-3/4

\$1.99 Each

HANDY/UTILITY

Bracket Boxes

1/2" K.O.S 2-1/2" DEEP

- Side K.O.s: (8) 1/2"
- Bottom K.O.s: (3) 1/2"
- Std. Pkg: 50




Item: 4SSLD-1/2



\$5.99 Each

1/2" & 3/4" K.O.S 1-7/8" DEEP

- Side K.O.s: (2) 1/2", (3) 1/2"-3/4"
- Bottom K.O.s: (2) 1/2", (1) 1/2"-3/4"
- Bracket: Right-angle, 1/2" setback
- Std. Pkg: 25



Item: G19281-AB



\$2.29 Each

AB BRACKET

1/2" K.O.S 1-7/8" DEEP

- Side K.O.s: (5) 1/2"
- Bottom K.O.s: (3) 1/2"
- Bracket: Flat vertical, 1/2" setback
- Std. Pkg: 25



Item: G19281-F




\$1.79 Each

F BRACKET

1/2" & 3/4" K.O.S 2-1/8" DEEP

- Side K.O.s: (2) 1/2", (3) 1/2"-3/4"
- Bottom K.O.s: (2) 1/2", (1) 1/2"-3/4"
- Bracket: Right-angle, 1/2" setback
- Std. Pkg: 25



Item: G19282-AB




\$3.99 Each

AB BRACKET

**1/2" K.O.S
2-1/8" DEEP**

- Side K.O.s: (5) 1/2"
- Bottom K.O.s: (3) 1/2"
- Bracket: Flat vertical, 1/2" setback
- Std. Pkg: 25



F BRACKET

Item: G19282-F



\$2.99 Each

**1/2" K.O.S
EXTENSION RING
1-1/2" DEEP**

- Side K.O.s: (8) 1/2"
- Std. Pkg: 50



Item: G19280-E

\$1.79 Each

**1/2" K.O.S
EXTENSION RING
1-7/8" DEEP**

- Side K.O.s: (8) 1/2"
- Std. Pkg: 50



Item: G19281-E

\$1.59 Each

**STAINLESS STEEL
1/2" K.O.S
EXTENSION RING
1-7/8" DEEP**

- Side K.O.s: (8) 1/2"
- Std. Pkg: 10



Item: G19281-ESS

\$25.99 Each

**STAINLESS STEEL
1/2" K.O.S
EXTENSION RING
2-1/8" DEEP**

- Side K.O.s: (8) 1/2"
- Std. Pkg: 10



Item: G19282-ESS

\$25.99 Each

OVERSIZED HANDY BOX

- 4-1/8" H x 2-1/8" W x 1-7/8" D
- Side K.O.s: (8) 1/2"
- Bottom K.O.s: (2) 1/2"
- Std. Pkg: 50



Item: G20281



\$3.99 Each

SWITCH BOXES

1-1/2" Deep

TAN DOOR-JAMB SWITCH KIT

- Includes box, plate, switch & wire leads
- Complete kit ready to install
- Std. Pkg: 10



Item: **DJSK**

\$11.99 Each

WHITE DOOR-JAMB SWITCH KIT

- Includes box, plate, switch & wire leads
- Complete kit ready to install
- Std. Pkg: 10



Item: **DJSKWH**

\$18.99 Each

1/2" K.O.S GANGABLE 1-1/2" DEEP

- Side K.O.s: (6) 1/2"
- Bottom K.O.s: (2) 1/2"
- Std. Pkg: 50



Item: **G500**

\$2.19 Each

1/2" K.O.S GANGABLE, "CUT-IN" 1-1/2" DEEP

- Side K.O.s: (6) 1/2"
- Bottom K.O.s: (2) 1/2"
- Old-Work clips
- Std. Pkg: 50




Item: **G500-OW**

\$3.19 Each

MC CABLE CLAMPS GANGABLE 1-1/2" DEEP

- Clamps: (4) Flexible metal conduit
- Bottom K.O.s: (1) 1/2"
- Std. Pkg: 50




Item: **G500-BX**

\$3.59 Each

MC CABLE CLAMPS GANGABLE "CUT-IN" 1-1/2" DEEP

- Clamps: (4) Flexible metal conduit
- Side K.O.s: (6) 1/2"
- Bottom K.O.s: (1) 1/2"
- Old-Work clips
- Std. Pkg: 50



Item: **G500-OWBX**

\$3.99 Each

NM CABLE CLAMPS GANGABLE 1-1/2" DEEP

- Clamps: (4) NM cable
- Bottom K.O.s: (1) 1/2"
- Std. Pkg: 50




Item: **G500-R**

\$1.99 Each

NM CABLE CLAMPS GANGABLE "CUT-IN" 1-1/2" DEEP

- Clamps: (4) NM cable
- Bottom K.O.s: (1) 1/2"
- Old-Work clips
- Std. Pkg: 50



Item: **G500-OWR**

\$3.99 Each

SWITCH BOXES

1-1/2" to 2-1/4" Deep

1/2" K.O.S GANGABLE 2" DEEP

- Side K.O.s: (6) 1/2"
- Bottom K.O.s: (2) 1/2"
- Std. Pkg: 50



Item: G600



\$2.49 Each

1/2" K.O.S GANGABLE "CUT-IN" 2" DEEP

- Side K.O.s: (6) 1/2"
- Bottom K.O.s: (2) 1/2"
- Old-Work clips
- Std. Pkg: 50




Item: G600-OW



\$3.49 Each

MC CABLE CLAMPS GANGABLE 2" DEEP

- Clamps: (4) Flexible metal conduit
- Bottom K.O.s: (1) 1/2"
- Std. Pkg: 50




Item: G600-BX



\$3.69 Each

MC CABLE CLAMPS GANGABLE "CUT-IN" 2" DEEP

- Clamps: (4) Flexible metal conduit
- Side K.O.s: (6) 1/2"
- Bottom K.O.s: (1) 1/2"
- Old-Work clips
- Std. Pkg: 50



Item: G600-OWBX

\$3.89 Each

NM CABLE CLAMPS GANGABLE 2" DEEP

- Clamps: (4) NM cable
- Bottom K.O.s: (1) 1/2"
- Std. Pkg: 50




Item: G600-R



\$2.49 Each

NM CABLE CLAMPS GANGABLE "CUT-IN" 2" DEEP

- Clamps: (4) NM cable
- Bottom K.O.s: (1) 1/2"
- Old-Work clips
- Std. Pkg: 50




Item: G600-OWR

\$3.89 Each

NM CABLE CLAMPS 2-1/4" DEEP

- Clamps: (4) NM cable
- Bottom K.O.s: (1) 1/2"
- Beveled back
- Std. Pkg: 50




Item: G601BVR



\$1.99 Each

NM CABLE CLAMPS GANGABLE "CUT-IN" 2-1/4" DEEP

- Clamps: (4) NM cable
- Bottom K.O.s: (1) 1/2"
- Beveled back, old-work clips
- Std. Pkg: 50



Item: G601BVR0W



\$3.39 Each

SWITCH BOXES

2-1/2" Deep

1/2" K.O.S GANGABLE 2-1/2" DEEP

- Side K.O.s: (6) 1/2"
- Bottom K.O.s: (2) 1/2"
- Std. Pkg: 50



Item: G601

\$1.89 Each

3/4" K.O.S GANGABLE 2-1/2" DEEP

- Side K.O.s: (6) 3/4"
- Bottom K.O.s: (2) 3/4"
- Std. Pkg: 50




Item: G601-3/4

\$3.49 Each

1/2" K.O.S GANGABLE "CUT-IN" 2-1/2" DEEP

- Side K.O.s: (6) 1/2"
- Bottom K.O.s: (2) 1/2"
- Old-Work clips
- Std. Pkg: 50



Item: G601-OW

\$2.99 Each

1/2" K.O.S BRACKETED 2-1/2" DEEP

- Side K.O.s: (4) 1/2"
- Bottom K.O.s: (2) 1/2"
- Bracket: Flat vertical
- Std. Pkg: 25




Item: G601-F

\$2.69 Each

MC CABLE CLAMPS GANGABLE 2-1/2" DEEP

- Clamps: (4) Flexible metal conduit
- Bottom K.O.s: (1) 1/2"
- Std. Pkg: 50



Item: G601-BX

\$2.99 Each

MC CABLE CLAMPS BRACKETED 2-1/2" DEEP

- Clamps: (4) Flexible metal conduit
- Side K.O.s: (4) 1/2"
- Bottom K.O.s: (1) 1/2"
- Bracket: Flat vertical
- Std. Pkg: 50




Item: G601-FBX

\$3.29 Each

MC CABLE CLAMPS GANGABLE "CUT-IN" 2-1/2" DEEP

- Clamps: (4) Flexible metal conduit
- Side K.O.s: (6) 1/2"
- Bottom K.O.s: (1) 1/2"
- Old-Work clips
- Std. Pkg: 50



Item: G601-OWBX

\$3.99 Each

NM CABLE CLAMPS GANGABLE 2-1/2" DEEP

- Clamps: (4) NM cable
- Bottom K.O.s: (1) 1/2"
- Std. Pkg: 50



Item: G601-R

\$2.49 Each

SWITCH BOXES

2-1/2" to 2-3/4" Deep

NM CABLE CLAMPS BRACKETED 2-1/2" DEEP

- Clamps: (4) NM cable
- Side K.O.s: (4) 1/2"
- Bottom K.O.s: (1) 1/2"
- Bracket: Flat vertical
- Std. Pkg: 50




Item: G601-FR



\$2.19 Each

NM CABLE CLAMPS GANGABLE "CUT-IN" 2-1/2" DEEP

- Clamps: (4) NM cable
- Bottom K.O.s: (1) 1/2"
- Old-Work clips
- Std. Pkg: 50



Item: G601-OWR

\$3.99 Each

1/2" & 3/4" K.O.S NONGANGABLE "CUT-IN" 2-1/2" DEEP

- Side K.O.s: (7) 1/2"-3/4"
- Bottom K.O.s: (2) 1/2"-3/4"
- Old-Work clips
- Std. Pkg: 25




Item: TB-125-OW

\$4.99 Each

1/2" K.O.S GANGABLE 2-3/4" DEEP

- Side K.O.s: (6) 1/2"
- Bottom K.O.s: (2) 1/2"
- Std. Pkg: 50




Item: G602



\$2.09 Each

1/2" K.O.S BRACKETED 2-3/4" DEEP

- Side K.O.s: (4) 1/2"
- Bottom K.O.s: (2) 1/2"
- Bracket: Flat vertical
- Std. Pkg: 50



Item: G602-F



\$3.99 Each

3/4" K.O.S GANGABLE 2-3/4" DEEP

- Side K.O.s: (6) 3/4"
- Bottom K.O.s: (2) 3/4"
- Std. Pkg: 50



Item: G602-3/4



\$3.99 Each

1/2" K.O.S GANGABLE "CUT-IN" 2-3/4" DEEP

- Side K.O.s: (6) 1/2"
- Bottom K.O.s: (2) 1/2"
- Old-Work clips
- Std. Pkg: 50



Item: G602-OW



\$3.19 Each

MC CABLE CLAMPS GANGABLE 2-3/4" DEEP

- Clamps: (4) Flexible metal conduit
- Side K.O.s: (6) 1/2"
- Bottom K.O.s: (1) 1/2"
- Std. Pkg: 50



Item: G602-BX



\$3.19 Each

CONDUIT BOXES

SWITCH BOXES

2-3/4" to 3-1/2" Deep

MC CABLE CLAMPS BRACKETED 2-1/2" DEEP

- Clamps: (4) Flexible metal conduit
- Side K.O.s: (4) 1/2"
- Bottom K.O.s: (1) 1/2"
- Bracket: Flat vertical
- Std. Pkg: 50




Item: G602-FBX

\$3.49 Each

1/2" K.O.S GANGABLE "CUT-IN" 2-3/4" DEEP

- Clamps: (4) Flexible metal conduit
- Side K.O.s: (6) 1/2"
- Bottom K.O.s: (1) 1/2"
- Old-Work clips
- Std. Pkg: 50



Item: G602-OWBX

\$3.99 Each

NM CABLE CLAMPS GANGABLE 2-3/4" DEEP

- Clamps: (4) NM cable
- Side K.O.s: (6) 1/2"
- Bottom K.O.s: (1) 1/2"
- Std. Pkg: 50




Item: G602-R

\$2.69 Each

NM CABLE CLAMPS BRACKETED 2-3/4" DEEP

- Clamps: (4) NM cable
- Side K.O.s: (4) 1/2"
- Bottom K.O.s: (1) 1/2"
- Bracket: Flat vertical
- Std. Pkg: 25




Item: G602-FR

\$2.99 Each

NM CABLE CLAMPS GANGABLE "CUT-IN" 2-3/4" DEEP

- Clamps: (4) NM cable
- Bottom K.O.s: (1) 1/2"
- Old-Work clips
- Std. Pkg: 50




Item: G602-OWR

\$3.99 Each

1/2" K.O.S GANGABLE 3-1/2" DEEP

- Side K.O.s: (6) 1/2"
- Bottom K.O.s: (2) 1/2"
- Std. Pkg: 25



Item: G603

\$2.19 Each

1/2" K.O.S BRACKETED 3-1/2" DEEP

- Side K.O.s: (4) 1/2"
- Bottom K.O.s: (2) 1/2"
- Bracket: Flat vertical
- Std. Pkg: 25



Item: G603-F

\$5.99 Each

3/4" K.O.S GANGABLE 3-1/2" DEEP

- Side K.O.s: (8) 3/4"
- Bottom K.O.s: (2) 3/4"
- Std. Pkg: 25



Item: G603-3/4


\$4.19 Each

SWITCH BOXES

3-1/2" Deep

1/2" K.O.S GANGABLE "CUT-IN" 3-1/2" DEEP

- Side K.O.s: (6) 1/2"
- Bottom K.O.s: (2) 1/2"
- Old-Work clips
- Preinstalled ground wire
- Std. Pkg: 25




Item: G603-OW

\$3.49 Each

MC CABLE CLAMPS GANGABLE 3-1/2" DEEP

- Clamps: (4) Flexible metal conduit
- Side K.O.s: (6) 1/2"
- Bottom K.O.s: (1) 1/2"
- Std. Pkg: 25



Item: G603-BX



\$3.29 Each

MC CABLE CLAMPS BRACKETED 3-1/2" DEEP

- Clamps: (4) Flexible metal conduit
- Side K.O.s: (4) 1/2"
- Bottom K.O.s: (1) 1/2"
- Bracket: Flat vertical
- Std. Pkg: 25




Item: G603-FBX

\$3.99 Each

MC CABLE CLAMPS GANGABLE "CUT-IN" 3-1/2" DEEP

- Clamps: (4) Flex metal conduit
- Side K.O.s: (6) 1/2"
- Bottom K.O.s: (1) 1/2"
- Old-Work clips
- Std. Pkg: 25



Item: G603-OWBX

\$4.99 Each

NM CABLE CLAMPS GANGABLE 3-1/2" DEEP

- Clamps: (4) NM cable
- Side K.O.s: (6) 1/2"
- Bottom K.O.s: (1) 1/2"
- Std. Pkg: 25



Item: G603-R

\$3.29 Each

NM CABLE CLAMPS BRACKETED 3-1/2" DEEP

- Clamps: (4) NM cable
- Side K.O.s: (4) 1/2"
- Bottom K.O.s: (1) 1/2"
- Bracket: Flat vertical
- Std. Pkg: 25




Item: G603-FR

\$2.99 Each

NM CABLE CLAMPS GANGABLE "CUT-IN" 3-1/2" DEEP

- Clamps: (4) NM cable
- Bottom K.O.s: (1) 1/2"
- Old-Work clips
- Std. Pkg: 25




Item: G603-OWR

\$4.99 Each

1/2" & 3/4" K.O.S NON-GANGABLE "CUT-IN" 3-1/2" DEEP

- Side K.O.s: (7) 1/2"-3/4"
- Bottom K.O.s: (2) 1/2"-3/4"
- Old-Work clips
- Std. Pkg: 25



Item: TB-135-OW

\$5.99 Each


CONDUIT BOXES

MULTI-GANG SWITCH

2-1/8" to 3-1/2" Deep

DIVIDER PLATE FOR 3-1/2" DEEP SWITCH BOXES

- Std. Pkg: 25



Item: GBD-350

\$1.29 Each

TWO-GANG 2-1/8" DEEP

- Side K.O.s: (4) 1/2", (4) 1/2"-3/4"
- Bottom K.O.s: (4) 1/2", (2) 3/4"
- Std. Pkg: 25



Item: MGSB-2



\$4.89 Each

TWO-GANG CUT-IN 2-1/8" DEEP

- Side K.O.s: (4) 1/2", (4) 1/2"-3/4"
- Bottom K.O.s: (3) 1/2", (2) 3/4"
- Old-Work clips for easy mounting in hollow wall
- Std. Pkg: 25



Item: MGSB-20W



\$7.99 Each

TWO-GANG BRACKETED 2-1/8" DEEP

- Side K.O.s: (3) 1/2", (4) 1/2"-3/4"
- Bottom K.O.s: (3) 1/2", (2) 3/4"
- Flat vertical bracket, 1/2" setback
- Std. Pkg: 25



Item: MGSB-2F



\$6.99 Each

THREE-GANG 2-1/8" DEEP

- Side K.O.s: (4) 1/2", (6) 1/2"-3/4"
- Bottom K.O.s: (3) 1/2", (2) 3/4"
- Std. Pkg: 25




Item: MGSB-3



\$7.99 Each

THREE-GANG CUT-IN 2-1/8" DEEP

- Side K.O.s: (6) 1/2"-3/4"
- Bottom K.O.s: (3) 1/2", (2) 3/4"
- Old-Work clips for easy mounting in hollow wall
- Std. Pkg: 25



Item: MGSB-30W



\$11.99 Each

THREE-GANG BRACKETED 2-1/8" DEEP

- Side K.O.s: (1) 1/2", (6) 1/2"-3/4"
- Bottom K.O.s: (3) 1/2", (2) 3/4"
- Flat vertical bracket, 1/2" setback
- Std. Pkg: 20




Item: MGSB-3F



\$8.99 Each

THREE-GANG WITH BRACKET 2-1/2" DEEP

- Side K.O.s: (8) 1/2"-3/4"
- Bottom K.O.s: (6) 1/2"-3/4"
- Flat vertical bracket, 1/2" setback
- Std. Pkg: 5



Item: TB-325-F



\$7.99 Each

MULTI-GANG SWITCH

2-1/8" to 3-1/2" Deep

THREE-GANG WITH BRACKET 3-1/2" DEEP

- Side K.O.s: (14) 1/2"-3/4"
- Bottom K.O.s: (6) 1/2"-3/4"
- Flat vertical bracket, 1/2" setback
- Std. Pkg: 5



Item: TB-335-F



\$11.49 Each

FOUR-GANG 2-1/8" DEEP

- Side K.O.s: (4) 1/2", (8) 1/2"-3/4"
- Bottom K.O.s: (5) 1/2", (3) 3/4"
- Std. Pkg: 20



Item: MGSB-4



\$10.99 Each

FOUR-GANG CUT-IN 2-1/8" DEEP

- Side K.O.s: (8) 1/2"-3/4"
- Bottom K.O.s: (5) 1/2", (3) 3/4"
- Old-Work clips for easy mounting in hollow wall
- Std. Pkg: 20



Item: MGSB-40W



\$14.99 Each

FOUR-GANG BRACKETED 2-1/8" DEEP

- Side K.O.s: (2) 1/2", (8) 1/2"-3/4"
- Bottom K.O.s: (5) 1/2", (3) 3/4"
- Flat vertical bracket, 1/2" setback
- Std. Pkg: 5



Item: MGSB-4F



\$11.99 Each

FOUR-GANG BRACKETED 2-1/2" DEEP

- Side K.O.s: (10) 1/2"-3/4"
- Bottom K.O.s: (6) 1/2"-3/4"
- Flat vertical bracket, 1/2" setback
- Std. Pkg: 5



Item: TB-425-F

\$9.99 Each

FOUR-GANG BRACKETED 3-1/2" DEEP

- Side K.O.s: (18) 1/2"-3/4"
- Bottom K.O.s: (8) 1/2"-3/4"
- Flat vertical bracket, 1/2" setback
- Std. Pkg: 5




Item: TB-435-F

\$14.99 Each

FIVE-GANG BRACKETED 2-1/2" DEEP

- Side K.O.s: (12) 1/2"-3/4"
- Bottom K.O.s: (6) 1/2"-3/4"
- Flat vertical bracket, 1/2" setback
- Std. Pkg: 5



Item: TB-525-F

\$11.99 Each

FAST CUSTOM BOXES!



CALL 847-455-0188

SWITCH BOX ACCESSORIES

All Styles

“CUT-IN” BOX OLD-WORK CLIPS

- Snaps on box edge and collapses behind drywall to secure box in hollow wall space
- Std. Pkg: 100 (50 pairs)




Item: OWC

\$0.69 Pair

“CUT-IN” BOX OLD-WORK EARS

- Screw-on ears attach to box and prevent box falling inside wall cavity.
- Std. Pkg: 100



Item: OWE

\$0.22 Each

SWITCHBOX SUPPORTS FOR HOLLOW WALLS

- 1-7/8" legs for standard-thickness walls
- Galvanized steel
- Std. Pkg: 100 Pairs



Item: SBS

\$0.49 Pair

EXTRA-LONG SWITCHBOX SUPPORTS FOR HOLLOW WALLS

- 2-1/2" legs for extra-thick walls
- Galvanized steel
- Std. Pkg: 100 Pairs



Item: SBS-L

\$0.59 Pair

SWITCHBOX EXTENSION RING

- Adds capacity to existing boxes
- Telescoping design allows adjustment to proper wall depth
- Std. Pkg: 50



Item: SBEX

\$1.99 Each

TOGGLE SWITCH LOCK BRACKET

- Locks switch On/Off
- Steel construction
- Lock hole: 0.31"
- Std. Pkg: 10



(lock not included)



Item: TOGLOK

\$2.99 Each

RED TOGGLE SWITCH LOCK BRACKET

- Locks switch On/Off
- Steel construction
- Lock hole: 0.31"
- Std. Pkg: 10



Item: TOGLOKRD

\$3.29 Each

WHITE TOGGLE SWITCH LOCK BRACKET

- Locks switch On/Off
- Steel construction
- Lock hole: 0.31"
- Std. Pkg: 10



Item: TOGLOKWH

\$3.29 Each

MASONRY BOXES

2-1/2" Deep

ONE-GANG SOLID 2-1/2" DEEP

- Side K.O.s: (6) 1/2"-3/4"
- Bottom K.O.s: (2) 1/2"-3/4"
- Std. Pkg: 20



Item: TB-125



\$3.89 Each

ONE-GANG GANGABLE 2-1/2" DEEP

- Side K.O.s: (6) 1/2"-3/4"
- Bottom K.O.s: (2) 1/2"-3/4"
- Std. Pkg: 20



Item: TB-125-G



\$2.79 Each

TWO-GANG SOLID 2-1/2" DEEP

- Side K.O.s: (8) 1/2"-3/4"
- Bottom K.O.s: (4) 1/2"-3/4"
- Std. Pkg: 10



Item: TB-225



\$5.29 Each

TWO-GANG GANGABLE 2-1/2" DEEP

- Side K.O.s: (8) 1/2"-3/4"
- Bottom K.O.s: (4) 1/2"-3/4"
- Std. Pkg: 10



Item: TB-225-G



\$5.49 Each

THREE-GANG SOLID 2-1/2" DEEP

- Side K.O.s: (10) 1/2"-3/4"
- Bottom K.O.s: (6) 1/2"-3/4"
- Std. Pkg: 10



Item: TB-325



\$6.49 Each

THREE-GANG GANGABLE 2-1/2" DEEP

- Side K.O.s: (10) 1/2"-3/4"
- Bottom K.O.s: (6) 1/2"-3/4"
- Std. Pkg: 10




Item: TB-325-G



\$6.89 Each

THREE-GANG VERTICAL BRACKET 2-1/2" DEEP

- Side K.O.s: (8) 1/2"-3/4"
- Bottom K.O.s: (6) 1/2"-3/4"
- Flat vertical bracket,
1/2" setback
- Std. Pkg: 5



Item: TB-325-F



\$7.99 Each

FOUR-GANG SOLID 2-1/2" DEEP

- Side K.O.s:
(12) 1/2"-3/4"
- Bottom K.O.s:
(8) 1/2"-3/4"
- Std. Pkg: 5



Item: TB-425



\$8.99 Each

MASONRY BOXES

2-1/2" Deep

FOUR-GANG GANGABLE 2-1/2" DEEP


- Side K.O.s:
(12) 1/2"-3/4"
- Bottom K.O.s:
(8) 1/2"-3/4"
- Std. Pkg: 5



Item: TB-425-G **\$9.99** Each

FOUR-GANG VERTICAL BRACKET 2-1/2" DEEP

- Side K.O.s:
(10) 1/2"-3/4"
- Bottom K.O.s:
(6) 1/2"-3/4"
- Flat vertical bracket,
1/2" setback
- Std. Pkg: 5



Item: TB-425-F **\$9.99** Each

FIVE-GANG SOLID 2-1/2" DEEP

- Side K.O.s:
(14) 1/2"-3/4"
- Bottom K.O.s:
(10) 1/2"-3/4"
- Std. Pkg: 5



Item: TB-525 **\$9.99** Each

FIVE-GANG GANGABLE 2-1/2" DEEP

- Side K.O.s:
(14) 1/2"-3/4"
- Bottom K.O.s:
(10) 1/2"-3/4"
- Std. Pkg: 5



Item: TB-525-G **\$10.99** Each

SIX-GANG SOLID 2-1/2" DEEP

- Side K.O.s:
(16) 1/2"-3/4"
- Bottom K.O.s:
(12) 1/2"-3/4"
- Std. Pkg: 1



Item: TB-625 **\$37.99** Each

SIX-GANG GANGABLE 2-1/2" DEEP

- Side K.O.s:
(16) 1/2"-3/4"
- Bottom K.O.s:
(12) 1/2"-3/4"
- Std. Pkg: 1



Item: TB-625-G **\$41.99** Each

SEVEN-GANG GANGABLE

- Std. Pkg: 1



ITEM	DEPTH	SIDE K.O.S BOTTOM K.O.S	PRICE EACH
TB-725-G	2-1/2"	(18) 1/2"-3/4" (14) 1/2"-3/4"	\$47.99



EIGHT-GANG GANGABLE

• Std. Pkg: 1



ITEM	DEPTH	SIDE K.O.S BOTTOM K.O.S	PRICE EACH
TB-825-G	2-1/2"	(20) 1/2"-3/4" (16) 1/2"-3/4"	\$51.99



NINE-GANG GANGABLE

• Std. Pkg: 1



ITEM	DEPTH	SIDE K.O.S BOTTOM K.O.S	PRICE EACH
TB-925-G	2-1/2"	(22) 1/2"-3/4" (18) 1/2"-3/4"	\$56.99



TEN-GANG GANGABLE

• Std. Pkg: 1



ITEM	DEPTH	SIDE K.O.S BOTTOM K.O.S	PRICE EACH
TB-1025-G	2-1/2"	(24) 1/2"-3/4" (20) 1/2"-3/4"	\$61.99



CALL FOR VOLUME DISCOUNTS!
847-455-0188

MASONRY BOXES

2-1/2" Deep Extension Rings

ONE-GANG EXTENSION RING 2-1/2" DEEP

- K.O.s: 1/2"-3/4"
- Includes 6-32 mounting screws
- Std. Pkg: 5



Item: TBX-125

\$19.99 Each

TWO-GANG EXTENSION RING 2-1/2" DEEP

- K.O.s: 1/2"-3/4"
- Includes 6-32 mounting screws
- Std. Pkg: 5



Item: TBX-225

\$26.99 Each

THREE-GANG EXTENSION RING 2-1/2" DEEP

- K.O.s: 1/2"-3/4"
- Includes 6-32 mounting screws
- Std. Pkg: 5



Item: TBX-325

\$34.99 Each

FOUR-GANG EXTENSION RING 2-1/2" DEEP

- K.O.s: 1/2"-3/4"
- Includes 6-32 mounting screws
- Std. Pkg: 5



Item: TBX-425

\$39.99 Each

FIVE-GANG EXTENSION RING 2-1/2" DEEP

- K.O.s: 1/2"-3/4"
- Includes 6-32 mounting screws
- Std. Pkg: 5



Item: TBX-525

\$47.99 Each

SIX-GANG EXTENSION RING 2-1/2" DEEP

- K.O.s: 1/2"-3/4"
- Includes 6-32 mounting screws
- Std. Pkg: 5



Item: TBX-625

\$61.99 Each

MASONRY BOXES

3-1/2" Deep

ONE-GANG SOLID 3-1/2" DEEP

- Side K.O.s: (8) 1/2"-3/4"
- Bottom K.O.s: (2) 1/2"-3/4"
- Std. Pkg: 20



Item: TB-135



\$3.99 Each

ONE-GANG GANGABLE 3-1/2" DEEP

- Side K.O.s: (8) 1/2"-3/4"
- Bottom K.O.s: (2) 1/2"-3/4"
- Std. Pkg: 20



Item: TB-135-G



\$3.49 Each

TWO-GANG SOLID 3-1/2" DEEP

- Side K.O.s: (12) 1/2"-3/4"
- Bottom K.O.s: (4) 1/2"-3/4"
- Std. Pkg: 10




Item: TB-235



\$5.99 Each

TWO-GANG GANGABLE 3-1/2" DEEP

- Side K.O.s: (12) 1/2"-3/4"
- Bottom K.O.s: (4) 1/2"-3/4"
- Std. Pkg: 10



Item: TB-235-G



\$6.59 Each

THREE-GANG SOLID 3-1/2" DEEP

- Side K.O.s: (16) 1/2"-3/4"
- Bottom K.O.s: (6) 1/2"-3/4"
- Std. Pkg: 10



Item: TB-335



\$7.99 Each

THREE-GANG GANGABLE 3-1/2" DEEP

- Side K.O.s: (16) 1/2"-3/4"
- Bottom K.O.s: (6) 1/2"-3/4"
- Std. Pkg: 5



Item: TB-335-G



\$8.79 Each

THREE-GANG VERTICAL BRACKET 3-1/2" DEEP

- Side K.O.s:
(14) 1/2"-3/4"
- Bottom K.O.s:
(6) 1/2"-3/4"
- Flat vertical bracket,
1/2" setback
- Std. Pkg: 5



Item: TB-335-F



\$11.49 Each

FOUR-GANG SOLID 3-1/2" DEEP

- Side K.O.s:
(20) 1/2"-3/4"
- Bottom K.O.s:
(8) 1/2"-3/4"
- Std. Pkg: 5



Item: TB-435



\$8.99 Each

MASONRY BOXES

3-1/2" Deep

FOUR-GANG GANGABLE 3-1/2" DEEP

- Side K.O.s:
(20) 1/2"-3/4"
- Bottom K.O.s:
(8) 1/2"-3/4"
- Std. Pkg: 5



Item: TB-435-G

\$9.99 Each

FOUR-GANG VERTICAL BRACKET 3-1/2" DEEP

- Side K.O.s:
(18) 1/2"-3/4"
- Bottom K.O.s:
(8) 1/2"-3/4"
- Flat vertical bracket,
1/2" setback
- Std. Pkg: 5




Item: TB-435-F

\$14.99 Each

FIVE-GANG SOLID 3-1/2" DEEP

- Side K.O.s:
(24) 1/2"-3/4"
- Bottom K.O.s:
(10) 1/2"-3/4"
- Std. Pkg: 1



Item: TB-535

\$14.99 Each

FIVE-GANG GANGABLE 3-1/2" DEEP

- Side K.O.s:
(24) 1/2"-3/4"
- Bottom K.O.s:
(10) 1/2"-3/4"
- Std. Pkg: 1



Item: TB-535-G

\$16.99 Each

SIX-GANG SOLID 3-1/2" DEEP

- Side K.O.s:
(28) 1/2"-3/4"
- Bottom K.O.s:
(12) 1/2"-3/4"
- Std. Pkg: 1



Item: TB-635

\$41.99 Each

SIX-GANG GANGABLE 3-1/2" DEEP

- Side K.O.s:
(28) 1/2"-3/4"
- Bottom K.O.s:
(12) 1/2"-3/4"
- Std. Pkg: 1



Item: TB-635-G

\$45.99 Each

SEVEN-GANG GANGABLE

- Std. Pkg: 1



ITEM	DEPTH	SIDE K.O.S BOTTOM K.O.S	PRICE EACH
TB-735-G	3-1/2"	(32) 1/2"-3/4" (14) 1/2"-3/4"	\$50.99



EIGHT-GANG GANGABLE

• Std. Pkg: 1



ITEM	DEPTH	SIDE K.O.S BOTTOM K.O.S	PRICE EACH
TB-835-G	3-1/2"	(36) 1/2"-3/4" (16) 1/2"-3/4"	\$55.99



NINE-GANG GANGABLE

• Std. Pkg: 1



ITEM	DEPTH	SIDE K.O.S BOTTOM K.O.S	PRICE EACH
TB-935-G	3-1/2"	(40) 1/2"-3/4" (18) 1/2"-3/4"	\$61.99



TEN-GANG GANGABLE

• Std. Pkg: 1



ITEM	DEPTH	SIDE K.O.S BOTTOM K.O.S	PRICE EACH
TB-1035-G	3-1/2"	(44) 1/2"-3/4" (20) 1/2"-3/4"	\$71.99



MASONRY BOXES

3-1/2" Deep Extension Rings

ONE-GANG EXTENSION RING 3-1/2" DEEP

- K.O.s: 1/2"-3/4"
- Includes 6-32 mounting screws
- Std. Pkg: 5



Item: TBX-135

\$22.99 Each

TWO-GANG EXTENSION RING 3-1/2" DEEP

- K.O.s: 1/2"-3/4"
- Includes 6-32 mounting screws
- Std. Pkg: 5



Item: TBX-235

\$33.99 Each

THREE-GANG EXTENSION RING 3-1/2" DEEP

- K.O.s: 1/2"-3/4"
- Includes 6-32 mounting screws
- Std. Pkg: 5



Item: TBX-335

\$39.99 Each

FOUR-GANG EXTENSION RING 3-1/2" DEEP

- K.O.s: 1/2"-3/4"
- Includes 6-32 mounting screws
- Std. Pkg: 5



Item: TBX-435

\$46.99 Each

FIVE-GANG EXTENSION RING 3-1/2" DEEP

- K.O.s: 1/2"-3/4"
- Includes 6-32 mounting screws
- Std. Pkg: 5



Item: TBX-535

\$54.99 Each

SIX-GANG EXTENSION RING 3-1/2" DEEP

- K.O.s: 1/2"-3/4"
- Includes 6-32 mounting screws
- Std. Pkg: 5



Item: TBX-635

\$69.99 Each

MASONRY BOXES

All Depths with Mortar Brackets

ONE-GANG MORTAR BRACKET 2-1/2" DEEP

- Bracket: Flat with mortar holes
- Std. Pkg: 25



Item: CB-1250

\$2.99 Each

ONE-GANG MORTAR BRACKET 3-1/2" DEEP

- Bracket: Flat with mortar holes
- Std. Pkg: 25



Item: CB-1350

\$2.99 Each

TWO-GANG MORTAR BRACKET 2-1/2" DEEP

- Bracket: Flat with mortar holes
- Std. Pkg: 10



Item: CB-2250

\$3.99 Each

TWO-GANG MORTAR BRACKET 3-1/2" DEEP

- Bracket: Flat with mortar holes
- Std. Pkg: 10



Item: CB-2350

\$3.99 Each

THREE-GANG MORTAR BRACKET 2-1/2" DEEP

- Bracket: Flat with mortar holes
- Std. Pkg: 10



Item: CB-3250

\$4.99 Each

THREE-GANG MORTAR BRACKET 3-1/2" DEEP

- Bracket: Flat with mortar holes
- Std. Pkg: 10




Item: CB-3350

\$4.99 Each

MASONRY BOX DEVICE SEPARATOR PARTITIONS

- Fits: 2-1/2" deep masonry boxes
- Std. Pkg: 50




Item: TBD-250

\$2.19 Each

MASONRY BOX DEVICE SEPARATOR PARTITIONS

- Fits: 3-1/2" deep masonry boxes
- Std. Pkg: 50



Item: TBD-350

\$3.29 Each

MULTI-GANG BOXES

1-5/8" Deep

TWO-GANG 1-5/8" DEEP

- Side K.O.s: (12) 1/2"-3/4"
- Bottom K.O.s: (4) 1/2", (2) 3/4"
- Std. Pkg: 25



Item: **GB-1582**

\$7.49 Each

THREE-GANG 1-5/8" DEEP

- Side K.O.s: (14) 1/2"-3/4"
- Bottom K.O.s: (6) 1/2", (4) 3/4"
- Std. Pkg: 20



Item: **GB-1583**

\$6.99 Each

FOUR-GANG 1-5/8" DEEP

- Side K.O.s: (16) 1/2"-3/4"
- Bottom K.O.s: (6) 1/2", (4) 3/4"
- Std. Pkg: 20



Item: **GB-1584**

\$10.99 Each

FIVE-GANG 1-5/8" DEEP

- Side K.O.s: (18) 1/2"-3/4"
- Bottom K.O.s: (6) 1/2", (4) 3/4"
- Std. Pkg: 10



Item: **GB-1585**

\$22.99 Each

SIX-GANG 1-5/8" DEEP

- Side K.O.s: (20) 1/2"-3/4"
- Bottom K.O.s: (6) 1/2", (4) 3/4"
- Std. Pkg: 5



Item: **GB-1586**

\$39.99 Each

SEVEN-GANG 1-5/8" DEEP

- Side K.O.s: (22) 1/2"-3/4"
- Bottom K.O.s: (6) 1/2", (4) 3/4"
- Std. Pkg: 5



Item: **GB-1587**

\$76.99 Each

EIGHT-GANG 1-5/8" DEEP

- Side K.O.s: (24) 1/2"-3/4"
- Bottom K.O.s: (6) 1/2", (4) 3/4"
- Std. Pkg: 5



Item: **GB-1588**

\$93.99 Each

NINE-GANG 1-5/8" DEEP

- Side K.O.s: (26) 1/2"-3/4"
- Bottom K.O.s: (6) 1/2", (4) 3/4"
- Std. Pkg: 5



Item: **GB-1589**

\$119.99 Each

MULTI-GANG BOXES

1-5/8" Deep Extension Rings

TWO-GANG 1-5/8" DEEP

- Side K.O.s:
(12) 1/2"-3/4"
- Std. Pkg: 25



Item: GBEX-1582  **\$47.99** Each

THREE-GANG 1-5/8" DEEP

- Side K.O.s:
(14) 1/2"-3/4"
- Std. Pkg: 20



Item: GBEX-1583  **\$53.99** Each

FOUR-GANG 1-5/8" DEEP

- Side K.O.s:
(16) 1/2"-3/4"
- Std. Pkg: 20



Item: GBEX-1584  **\$69.99** Each

FIVE-GANG 1-5/8" DEEP


- Side K.O.s:
(18) 1/2"-3/4"
- Std. Pkg: 10



Item: GBEX-1585  **\$92.99** Each

SIX-GANG 1-5/8" DEEP

- Side K.O.s:
(20) 1/2"-3/4"
- Std. Pkg: 5



Item: GBEX-1586  **\$146.99** Each

SEVEN-GANG 1-5/8" DEEP

- Side K.O.s:
(22) 1/2"-3/4"
- Std. Pkg: 5



Item: GBEX-1587  **\$212.99** Each

EIGHT-GANG 1-5/8" DEEP

- Side K.O.s:
(24) 1/2"-3/4"
- Std. Pkg: 5



Item: GBEX-1588  **\$249.99** Each

NINE-GANG 1-5/8" DEEP

- Side K.O.s:
(26) 1/2"-3/4"
- Std. Pkg: 5



Item: GBEX-1589  **\$279.99** Each

C
O
N
D
U
I
T

B
O
X
E
S

MULTI-GANG BOXES

2-1/2" Deep

TWO-GANG 2-1/2" DEEP

- Side K.O.s:
(12) 1/2"-3/4"
- Bottom K.O.s:
(4) 1/2", (2) 3/4"
- Std. Pkg: 25



Item: GB-2122

\$29.99 Each

TWO-GANG 3/4"-1" K.O.S 2-1/2" DEEP

- Side K.O.s: (8) 3/4"-1",
(4) 1/2"-3/4"
- Bottom K.O.s:
(4) 1/2", (2) 3/4"
- Std. Pkg: 25



Item: GB-2122341

\$32.99 Each

THREE-GANG 2-1/2" DEEP

- Side K.O.s:
(14) 1/2"-3/4"
- Bottom K.O.s:
(6) 1/2", (4) 3/4"
- Std. Pkg: 20



Item: GB-2123

\$21.99 Each

THREE-GANG 3/4"-1" K.O.S 2-1/2" DEEP

- Side K.O.s: (10) 3/4"-1",
(4) 1/2"-3/4"
- Bottom K.O.s:
(6) 1/2", (4) 3/4"
- Std. Pkg: 20



Item: GB-2123341

\$29.99 Each

FOUR-GANG 2-1/2" DEEP

- Side K.O.s:
(16) 1/2"-3/4"
- Bottom K.O.s:
(6) 1/2", (4) 3/4"
- Std. Pkg: 20



Item: GB-2124

\$21.99 Each

FOUR-GANG 3/4"-1" K.O.S 2-1/2" DEEP

- Side K.O.s: (12) 3/4"-1",
(4) 1/2"-3/4"
- Bottom K.O.s:
(6) 1/2", (4) 3/4"
- Std. Pkg: 20



Item: GB-2124341

\$34.99 Each

FIVE-GANG 2-1/2" DEEP

- Side K.O.s:
(18) 1/2"-3/4"
- Bottom K.O.s:
(6) 1/2", (4) 3/4"
- Std. Pkg: 10



Item: GB-2125

\$49.99 Each

FIVE-GANG 3/4"-1" K.O.S 2-1/2" DEEP

- Side K.O.s: (14) 3/4"-1",
(4) 1/2"-3/4"
- Bottom K.O.s:
(6) 1/2", (4) 3/4"
- Std. Pkg: 10



Item: GB-2125341

\$64.99 Each

MULTI-GANG BOXES

2-1/2" Deep

SIX-GANG 2-1/2" DEEP

- Side K.O.s:
(20) 1/2"-3/4"
- Bottom K.O.s:
(6) 1/2", (4) 3/4"
- Std. Pkg: 5



Item: GB-2126



\$109.99 Each

SIX-GANG 3/4"-1" K.O.S 2-1/2" DEEP

- Side K.O.s: (16) 3/4"-1",
(4) 1/2"-3/4"
- Bottom K.O.s:
(6) 1/2", (4) 3/4"
- Std. Pkg: 5



Item: GB-2126341

\$119.99 Each

SEVEN-GANG 2-1/2" DEEP

- Side K.O.s:
(22) 1/2"-3/4"
- Bottom K.O.s:
(6) 1/2", (4) 3/4"
- Std. Pkg: 5



Item: GB-2127



\$124.99 Each

SEVEN-GANG 3/4"-1" K.O.S 2-1/2" DEEP

- Side K.O.s:
(18) 3/4"-1",
(4) 1/2"-3/4"
- Bottom K.O.s:
(6) 1/2", (4) 3/4"
- Std. Pkg: 5



Item: GB-2127341

\$144.99 Each

EIGHT-GANG 2-1/2" DEEP

- Side K.O.s:
(24) 1/2"-3/4"
- Bottom K.O.s:
(6) 1/2", (4) 3/4"
- Std. Pkg: 5



Item: GB-2128



\$134.99 Each

EIGHT-GANG 3/4"-1" K.O.S 2-1/2" DEEP

- Side K.O.s:
(20) 3/4"-1",
(4) 1/2"-3/4"
- Bottom K.O.s:
(6) 1/2", (4) 3/4"
- Std. Pkg: 5



Item: GB-2128341

\$164.99 Each

NINE-GANG 2-1/2" DEEP

- Side K.O.s:
(26) 1/2"-3/4"
- Bottom K.O.s:
(6) 1/2", (4) 3/4"
- Std. Pkg: 5



Item: GB-2129



\$154.99 Each

NINE-GANG 3/4"-1" K.O.S 2-1/2" DEEP

- Side K.O.s:
(22) 3/4"-1",
(4) 1/2"-3/4"
- Bottom K.O.s:
(6) 1/2", (4) 3/4"
- Std. Pkg: 5



Item: GB-2129341


\$184.99 Each

MULTI-GANG BOXES

2-1/2" Deep Extension Rings

TWO-GANG 2-1/2" DEEP

- Side K.O.s:
(12) 1/2"-3/4"
- Std. Pkg: 25



Item: GBEX-2122 **\$64.99** Each

THREE-GANG 2-1/2" DEEP

- Side K.O.s:
(14) 1/2"-3/4"
- Std. Pkg: 20



Item: GBEX-2123 **\$73.99** Each

FOUR-GANG 2-1/2" DEEP

- Side K.O.s:
(16) 1/2"-3/4"
- Std. Pkg: 20



Item: GBEX-2124 **\$89.99** Each

FIVE-GANG 2-1/2" DEEP

- Side K.O.s:
(18) 1/2"-3/4"
- Std. Pkg: 10



Item: GBEX-2125 **\$119.99** Each

SIX-GANG 2-1/2" DEEP

- Side K.O.s:
(20) 1/2"-3/4"
- Std. Pkg: 5



Item: GBEX-2126 **\$166.99** Each

SEVEN-GANG 2-1/2" DEEP

- Side K.O.s:
(22) 1/2"-3/4"
- Std. Pkg: 5



Item: GBEX-2127 **\$234.99** Each

EIGHT-GANG 2-1/2" DEEP

- Side K.O.s:
(24) 1/2"-3/4"
- Std. Pkg: 5



Item: GBEX-2128 **\$285.99** Each

NINE-GANG 2-1/2" DEEP

- Side K.O.s:
(26) 1/2"-3/4"
- Std. Pkg: 5




Item: GBEX-2129 **\$299.99** Each

PAN BOXES

3-1/2" Round

3-1/2" ROUND PAN BOX, CONDUIT K.O.S

- Depth: 1/2"
- Std. Pkg: 50





ITEM	KNOCKOUTS	PRICE EACH
46111	(3) 1/2" (4) Pryouts	\$1.89




3-1/2" ROUND "CUT-IN" PAN BOX FOR HOLLOW WALLS

- Depth: 1/2"
- Does not protrude in wall cavity
- Std. Pkg: 50



IN-WALL OBSTRUCTIONS



NO PROBLEM!

ITEM	KNOCKOUTS	PRICE EACH
46111-OW	(2) 1/2"	\$4.29



3-1/2" ROUND FAN-RATED PAN BOX

- Depth: 3/4"
- Std. Pkg: 50




ITEM	KNOCKOUTS	PRICE EACH
46112	(2) 1/2" Fan Rated with mounting hardware	\$2.19



3-1/2" ROUND PAN BOX, NM CABLE CLAMPS

- Depth: 1/2"
- Std. Pkg: 50



ITEM	KNOCKOUTS	PRICE EACH
46111-R	(1) 1/2" (4) NM Cables	\$1.29



CONDUIT BOXES

PAN BOXES

4" Round

3-1/2" ROUND PAN BOX EXTENSION RING

- Depth: 1/2"
- Std. Pkg: 10



ITEM	KNOCKOUTS	PRICE EACH
47111	None Extension Ring	\$4.99



4" ROUND EXTRA-SHALLOW PAN BOX, CONDUIT K.O.S

- Depth: 1/4"
- Std. Pkg: 50



ITEM	KNOCKOUTS	PRICE EACH
56113	(5) 1/2"	\$4.99



- Great for drywall overlay on existing surface!

4" ROUND PAN BOX, CONDUIT K.O.S

- Depth: 1/2"
- Std. Pkg: 50




ITEM	KNOCKOUTS	PRICE EACH
56111	(5) 1/2"	\$2.29




4" ROUND "CUT-IN" PAN BOX FOR HOLLOW WALLS

- Depth: 1/2"
- Installs no deeper than drywall
- Std. Pkg: 50



PIPE OBSTRUCTIONS



NO PROBLEM!

ITEM	KNOCKOUTS	PRICE EACH
56111-OW	(2) 1/2" Old Work Clamp & Flange for "cut-in" to hollow wall	\$4.29



PAN BOXES

4" Round

4" ROUND FAN-RATED PAN BOX

- Depth: 1/2"
- Mounting hardware included
- Std. Pkg: 50




ITEM	KNOCKOUTS	PRICE EACH
56112	(2) 1/2"	\$3.99



4" ROUND PAN BOX NM CABLE CLAMPS

- Depth: 1/2"
- Std. Pkg: 50



ITEM	KNOCKOUTS	PRICE EACH
56111-R	(3) 1/2" & (4) NM Cables	\$2.49



4" ROUND PAN BOX EXTENSION RING

- Depth: 1/2"
- Std. Pkg: 50



ITEM	KNOCKOUTS	PRICE EACH
57111	None Extension Ring	\$4.99



CONDUIT BOXES

GARVIN
ELECTRICAL MANUFACTURER

Need A Special Part Made?

WE CUSTOMIZE

Boxes & Covers | Fittings | Hangers & Clamps



Fast Solutions... Designed By You!

4" OCTAGON BOXES

1-1/2" Deep

BLANK, NO K.O.S 1-1/2" DEEP

- Blank sides & bottom
- Std. Pkg: 50



Item: 54151-BLNK **\$6.99** Each

STAINLESS STEEL BLANK, NO K.O.S 1-1/2" DEEP

- Blank sides & bottom
- 314 Stainless steel
- Std. Pkg: 50



Item: 54151-BLNKSS **\$33.99** Each

1/2" K.O.S 1-1/2" DEEP

- K.O.s sides: (4) 1/2"
- K.O.s bottom: (5) 1/2"
- Std. Pkg: 50



Item: 54151-1/2  **\$0.89** Each

1/2" K.O.S 4 MOUNTING TABS 1-1/2" DEEP

- K.O.s sides: (4) 1/2"
- K.O.s bottom: (5) 1/2"
- (4) Threaded mounting tabs
- Std. Pkg: 50



Item: 54151-DE  **\$3.99** Each

1/2" AIR-TIGHT K.O.S 1-1/2" DEEP

- K.O.s sides: (4) 1/2"
- K.O.s bottom: (5) 1/2"
- Std. Pkg: 50



Item: 54151-VT  **\$5.99** Each

3/4" K.O.S 1-1/2" DEEP

- K.O.s sides: (4) 3/4"
- K.O.s bottom: (3) 1/2", (2) 3/4"
- Std. Pkg: 50



Item: 54151-3/4  **\$1.69** Each

1/2" & 3/4" K.O.S 1-1/2" DEEP

- K.O.s sides: (2) 1/2", (2) 3/4"
- K.O.s bottom: (3) 1/2", (2) 3/4"
- Std. Pkg: 50



Item: 54151-S  **\$0.99** Each

1/2" K.O.S CUT-IN 1-1/2" DEEP

- K.O.s sides: (2) 1/2"
- K.O.s bottom: (3) 1/2", (2) 3/4"
- Old-work clips & ears
- Std. Pkg: 50




Item: 54151-OW  **\$3.29** Each

4" OCTAGON BOXES

1- 1/2" Deep

1/2" K.O.S 4 MOUNTING TABS CUT-IN 1-1/2" DEEP

- K.O.s sides: (2) 1/2"
- K.O.s bottom: (3) 1/2", (2) 3/4"
- Old-work clips & ears
- (4) Threaded mounting tabs
- Std. Pkg: 50



Item: 54151-DEOW **\$3.99** Each

STAINLESS STEEL 1/2" & 3/4" VAPOR-TIGHT K.O.S 1-1/2" DEEP

- K.O.s sides: (2) 1/2", (2) 3/4"
- K.O.s bottom: (3) 1/2", (2) 3/4"
- Std. Pkg: 50



Item: 54151-SVTSS **\$33.99** Each

1/2" K.O.S FAN-RATED 1-1/2" DEEP


- Meets NEC 314.27
- Tested Max. Load: 500 Lbs.
- K.O.s sides: (4) 1/2"
- K.O.s bottom: (5) 1/2"
- Std. Pkg: 25



Item: 54151-FANNB **\$5.79** Each

1/2" K.O.S FAN-RATED WEATHERPROC 1-1/2" DEEP

- Meets NEC 314.27
- Tested Max. Load: 500 Lbs.
- K.O.s sides: (4) 1/2"
- K.O.s bottom: (5) 1/2"
- Std. Pkg: 25



Item: 54151-FANNBWP **\$9.99** Each

1/2" & 3/4" K.O.S 1-1/2" DEEP

- K.O.s sides: (2) 1/2", (2) 3/4"
- K.O.s bottom: (3) 1/2", (2) 3/4"z
- Painted Red
- Std. Pkg: 50



Item: 54151-RED **\$5.99** Each

MC CABLE CLAMPS 1-1/2" DEEP


- K.O.s sides: (2) 1/2", (4) BX/MC clamps
- K.O.s bottom: (1) 1/2"
- Std. Pkg: 50



Item: 54151-BX **\$2.49** Each

MC CABLE CLAMPS OLD-WORK CUT-IN 1-1/2" DEEP


- K.O.s sides: (4) BX/MC clamps
- K.O.s bottom: (1) 1/2"
- Old-work clips & ears
- Std. Pkg: 50



Item: 54151-OWBX **\$3.29** Each

NM CABLE CLAMPS 1-1/2" DEEP

- K.O.s sides: (2) 1/2", (4) NM clamps
- K.O.s bottom: (1) 1/2"
- Std. Pkg: 50



Item: 54151-R **\$2.39** Each

4" OCTAGON BOXES

1-1/2" Deep Bracket Boxes

1/2" K.O.S FAN-RATED BRACKET 1-1/2" DEEP

- Meets NEC 314.27
 - Tested Max. Load: 500 Lbs.
 - K.O.s sides: (3) 1/2"
 - K.O.s bottom: (3) 1/2", (2) 3/4"
 - Std. Pkg: 25
- Item: 54151-FAN**



\$5.99 Each

1/2" K.O.S FAN-RATED WEATHERPRO WITH BRACKET 1-1/2" DEEP

- Meets NEC 314.27
 - Tested Max. Load: 500 Lbs.
 - K.O.s sides: (3) 1/2"
 - K.O.s bottom: (5) 1/2"
 - Std. Pkg: 25
- Item: 54151-FANWP**



\$9.99 Each

1/2" K.O.S VERTICAL BRACKET 1-1/2" DEEP


- Side K.O.s: (3) 1/2"
 - K.O.s bottom: (3) 1/2", (2) 3/4"
 - 1/2" bracket setback
 - Std. Pkg: 25
- Item: 54151-F**



\$1.99 Each

MC CABLE CLAMPS VERTICAL BRACKET 1-1/2" DEEP


- Clamps: (4) BX/MC cable
 - Side K.O.s: (2) 1/2"
 - Bottom K.O.s: (1) 1/2"
 - 1/2" bracket setback
 - Std. Pkg: 25
- Item: 54151-FBX**



\$2.29 Each

NM CABLE CLAMPS VERTICAL BRACKET 1-1/2" DEEP


- Clamps: (4) NM cable
 - Side K.O.s: (2) 1/2"
 - Bottom K.O.s: (1) 1/2"
 - 1/2" bracket setback
 - Std. Pkg: 25
- Item: 54151-FR**



\$2.29 Each

1/2" K.O.S FLUSH-MOUNT BRACKET 1-1/2" DEEP


- Side K.O.s: (4) 1/2"
 - K.O.s bottom: (5) 1/2"
 - Nail-spiked bracked
 - Std. Pkg: 25
- Item: 54151-J**



\$2.29 Each

MC CABLE CLAMPS FLUSH-MOUNT BRACKET 1-1/2" DEEP


- Clamps: (4) BX/MC cable
 - Side K.O.s: (2) 1/2"
 - K.O.s bottom: (1) 1/2"
 - Nail-spiked bracked
 - Std. Pkg: 25
- Item: 54151-JBX**



\$2.79 Each

NM CABLE CLAMPS FLUSH-MOUNT BRACKET 1-1/2" DEEP

- Clamps: (4) NM cable
 - Side K.O.s: (2) 1/2"
 - Bottom K.O.s: (1) 1/2"
 - Nail-spiked bracked
 - Std. Pkg: 25
- Item: 54151-JR**



\$2.49 Each

4" OCTAGON BOXES

2-1/8" Deep

NM CABLE CLAMPS OLD-WORK CUT-IN 1-1/2" DEEP

- K.O.s sides: (4) NM clamps
- K.O.s bottom: (1) 1/2"
- Old-work clips & ears
- Std. Pkg: 25



Item: 54151-OWR



\$3.29 Each

BLANK, NO K.O.S 2-1/8" DEEP

- Blank sides & bottom
- Std. Pkg: 25



Item: 54171-BLNK

\$7.99 Each

STAINLESS STEEL BLANK, NO K.O.S 2-1/8" DEEP

- Blank sides & bottom
- 314 Stainless steel
- Std. Pkg: 25



Item: 54171-BLNKSS

\$37.99 Each

1/2" K.O.S 2-1/8" DEEP

- K.O.s sides: (4) 1/2"
- K.O.s bottom: (3) 1/2", (2) 3/4"
- Std. Pkg: 25



Item: 54171-1/2



\$2.49 Each

1/2" & 3/4" K.O.S 4 MOUNTING TABS 2-1/8" DEEP

- K.O.s sides: (2) 1/2", (2) 3/4"
- K.O.s bottom: (3) 1/2", (2) 3/4"
- (4) Threaded mounting tabs
- Std. Pkg: 25



Item: 54171-DE



\$4.29 Each

1/2" K.O.S CUT-IN 2-1/8" DEEP

- K.O.s sides: (2) 1/2"
- K.O.s bottom: (3) 1/2", (2) 3/4"
- Old-work clips & ears
- Std. Pkg: 25




Item: 54171-OW



\$4.99 Each

1/2" K.O.S 4 MOUNTING TABS CUT-IN 2-1/8" DEEP

- K.O.s sides: (2) 1/2"
- K.O.s bottom: (3) 1/2", (2) 3/4"
- Old-work clips & ears
- Std. Pkg: 25



Item: 54171-DEOW



\$4.69 Each

3/4" K.O.S 2-1/8" DEEP

- K.O.s sides: (4) 3/4"
- K.O.s bottom: (3) 1/2", (2) 3/4"
- Std. Pkg: 25



Item: 54171-3/4



\$2.79 Each

4" OCTAGON BOXES

2-1/8" Deep

1/2" & 3/4" K.O.S 2-1/8" DEEP

- K.O.s sides: (2) 1/2", (2) 3/4"
- K.O.s bottom: (3) 1/2", (2) 3/4"
- Std. Pkg: 25



Item: 54171-S  **\$1.99** Each


1/2" K.O.S FAN-RATED 2-1/8" DEEP



- Meets NEC 314.27
- Tested Max. Load: 500 Lbs.
- K.O.s sides: (4) 1/2"
- K.O.s bottom: (5) 1/2"
- Std. Pkg: 25

Item: 54171-FANNB  **\$6.99** Each

1/2" K.O.S FAN-RATED WEATHERPROOF 2-1/8" DEEP



- Meets NEC 314.27
- Tested Max. Load: 500 Lbs.
- K.O.s Sides: (4) 1/2"; Bottom: (5) 1/2"
- Std. Pkg: 25

Item: 54171-FANNBWP  **\$9.99** Each

1/2" & 3/4" AIR-TIGHT K.O.S 2-1/8" DEEP



- K.O.s sides: (2) 1/2", (2) 3/4"
- K.O.s bottom: (3) 1/2", (2) 3/4"
- Std. Pkg: 25

Item: 54171-SVT  **\$5.99** Each

STAINLESS STEEL 1/2" & 3/4" VAPOR-TIGHT K.O.S 2-1/8" DEEP



- K.O.s sides: (2) 1/2", (2) 3/4"
- K.O.s bottom: (3) 1/2", (2) 3/4"
- Std. Pkg: 25

Item: 54171-SVTSS  **\$37.99** Each

BLANK BOTTOM 2-1/8" DEEP



- K.O.s sides: (2) 1/2", (2) 3/4"
- Blank bottom
- Std. Pkg: 25

Item: 54171-SBB **\$7.99** Each

1/2" & 3/4" K.O.S 2-1/8" DEEP


- K.O.s sides: (2) 1/2", (2) 1/2"-3/4"
- K.O.s bottom: (3) 1/2", (2) 3/4"
- Painted: Red
- Std. Pkg: 25



Item: 54171-RED **\$7.99** Each

MC CABLE CLAMPS 2-1/8" DEEP

- K.O.s sides: (2) 1/2", (4) BX/MC cable clamps
- K.O.s bottom: (1) 1/2"
- Std. Pkg: 25



Item: 54171-BX  **\$3.49** Each

4" OCTAGON BOXES

2-1/8" & 3-1/2" Deep

MC CABLE CLAMPS

CUT-IN

2-1/8" DEEP

- K.O.s sides: (4) BX/MC cable clamps
- K.O.s bottom: (1) 1/2"
- Old-work clips & ears
- Std. Pkg: 25



Item: 54171-OWBX

\$5.99 Each

NM CABLE CLAMPS

2-1/8" DEEP

- K.O.s sides: (2) 1/2", (4) NM clamps
- K.O.s bottom: (1) 1/2"
- Std. Pkg: 25



Item: 54171-R

\$2.59 Each




NM CABLE CLAMPS

CUT-IN

2-1/8" DEEP

- K.O.s sides: (4) NM clamps
- K.O.s bottom: (1) 1/2"
- Old-work clips & ears
- Std. Pkg: 25



Item: 54171-OWR

\$5.99 Each

OPEN-SPLICE BOX

2-1/8" DEEP

- (8) side slots for insertion of NM cable open splices
- NM cable clamps, removeable side panels
- Cover included
- Std. Pkg: 25



Item: 54171-OPR


\$6.99 Each



T-BAR CEILING-GRID

2-1/8" DEEP

- Sides: (4) T-Bar slots
- K.O.s bottom: (2) 1/2"
- Backside eyelet for wire support
- Std. Pkg: 25



Item: 54171-TBAR

\$8.99 Each



FAN-RATED CEILING-GRID BOX

2-1/8" DEEP

- K.O.s sides: (4) T-Bar slots, (2) 1/2" Fan-rated ears
- K.O.s bottom: (2) 1/2"
- Std. Pkg: 25



Item: 54171-TBFN


\$15.99 Each



BLANK, NO K.O.S

3-1/2" DEEP

- Blank sides & bottom
- Std. Pkg: 25




Item: 54181-BLNK

\$9.99 Each

1/2" & 3/4" K.O.S

3-1/2" DEEP

- K.O.s sides: (4) 1/2"-3/4"
- K.O.s bottom: (3) 1/2", (2) 3/4"
- Std. Pkg: 25



Item: 54181-S

\$8.99 Each




4" OCTAGON BOXES

3-1/2" Deep

T-BAR CEILING-GRID

3-1/2" DEEP

- K.O.s sides: (4) T-Bar slots, (4) 1/2"-3/4"
- K.O.s bottom: (2) 1/2"
- External bottom eyelet for wire support
- Std. Pkg: 10



Item: 54181-TBAR


\$13.99 Each

1/2" K.O.S

CUT-IN

3-1/2" DEEP

- K.O.s sides: (4) 1/2"-3/4"
- K.O.s bottom: (3) 1/2", (2) 3/4"
- Old-work clips included
- Std. Pkg: 25



Item: 54181-OW



\$8.99 Each

Extension Rings

BLANK, NO K.O.S

EXTENSION RING

1-1/2" DEEP

- Blank sides & bottom
- Std. Pkg: 50



Item: 55151-BLNKSS

\$36.99 Each

1/2" K.O.S

EXTENSION RING

1-1/2" DEEP

- K.O.s sides: (4) 1/2"
- Std. Pkg: 50



Item: 55151-1/2



\$1.79 Each

1/2" K.O.S

AIR-TIGHT PLENUM

EXTENSION RING

1-1/2" DEEP

- K.O.s sides: (4) 1/2"
- Std. Pkg: 50



Item: 55151-VT



\$7.99 Each

3/4" K.O.S

EXTENSION RING

1-1/2" DEEP

- K.O.s sides: (4) 3/4"
- Std. Pkg: 50



Item: 55151-3/4



\$2.59 Each

1/2" & 3/4" K.O.S

EXTENSION RING

1-1/2" DEEP

- K.O.s sides: (2) 1/2", (2) 3/4"
- Std. Pkg: 50



Item: 55151-S



\$1.99 Each

**NEED A
CUSTOM BOX
FAST!**

CALL 847-455-0188

4" OCTAGON

Extension Rings

STAINLESS STEEL 1/2" & 3/4" VAPOR-TIGHT K.O.S 1-1/2" DEEP

- K.O.s sides: (2) 1/2", (2) 3/4"
- Std. Pkg: 50



Item: 55151-SVTSS



\$35.99 Each

1/2" & 3/4" K.O.S EXTENSION RING 1-1/2" DEEP

- K.O.s sides: (2) 1/2", (2) 3/4"
- Painted: Red
- Std. Pkg: 50



Item: 55151-RED

\$6.99 Each

STAINLESS STEEL BLANK, NO K.O.S EXTENSION RING 2-1/8" DEEP

- Blank sides
- Std. Pkg: 50



Item: 55171-BLNKSS

\$39.99 Each

1/2" & 3/4" K.O.S EXTENSION RING 2-1/8" DEEP

- K.O.s sides: (2) 1/2", (2) 3/4"
- Std. Pkg: 25



Item: 55171-S

\$6.99 Each

1/2" & 3/4" AIR-TIGHT K.O.S EXTENSION RING 2-1/8" DEEP

- K.O.s sides: (2) 1/2", (2) 3/4"
- Std. Pkg: 25



Item: 55171-SVT

\$7.99 Each

1/2" & 3/4" K.O.S EXTENSION RING 2-1/8" DEEP

- K.O.s sides: (2) 1/2", (2) 3/4"
- Painted: Red
- Std. Pkg: 25




Item: 55171-RED

\$8.99 Each

1/2" & 3/4" K.O.S EXTENSION RING 3-1/2" DEEP

- K.O.s sides: (4) 1/2"-3/4"
- Std. Pkg: 10



Item: 55181-S

\$7.99 Each

CALL FOR VOLUME DISCOUNTS!


847-455-0188

4" OCTAGON BOXES

1-1/2" Deep Assemblies

4" OCTAGON FAN-RATED BOX WITH TELESCOPING "CUT-IN" BAR HANGER


- Box slides to any position
- Meets NEC 314.27
- Tested Max. Load: 500 Lbs.
- Std. Pkg: 25



1) Cut hole & insert bracket.



2) Twist out to bite on joists.




3) Install box.



ITEM	SIDE K.O.S BOTTOM K.O.S	BOX DEPTH	PRICE EACH
54151-FANOW	(4) 1/2" (2) 1/2"	1-1/2"	\$11.99

4" OCTAGON FAN-RATED BOX WITH NEW CONSTRUCTION BAR HANGER

- Box slides to any position
- Meets NEC 314.27
- Tested Max. Load: 500 Lbs.
- K.O.s sides: (4) 1/2" & 1/2" NM cable clamps
- Std. Pkg: 25



ITEM	BOX DEPTH	PRICE EACH
54151-FANBH	1-1/2"	\$8.99

4" OCTAGON BOXES

1-1/2" Deep Assemblies

1/2" & 3/4" K.O.S ADJUSTABLE BAR HANGER 1-1/2" DEEP



- 16"-24" adjustable
- Side K.O.s: (4) 1/2"
- K.O.s bottom: (2) 1/2", (2) 3/4"
- Std. Pkg: 25

Item: 54151-HU

\$3.99 Each




MC CABLE CLAMPS ADJUSTABLE BAR HANGER 1-1/2" DEEP



- 16"-24" adjustable
- Clamps: (4) BX/MC
- Side K.O.s: (2) 1/2"
- Std. Pkg: 25

Item: 54151-HUBX

\$4.99 Each



NM CABLE CLAMPS ADJUSTABLE BAR HANGER 1-1/2" DEEP

- 16"-24" adjustable
- Clamps: (4) NM cable
- Side K.O.s: (2) 1/2"
- Std. Pkg: 25

Item: 54151-HUR

\$4.99 Each




CONDUIT BOXES

GARVIN
ELECTRICAL MANUFACTURER

Need A Special Part Made?

WE CUSTOMIZE

Boxes & Covers | Fittings | Hangers & Clamps




Fast Solutions... Designed By You!

4" OCTAGON BOXES

2-1/8" Deep Assemblies

4" OCTAGON FAN-RATED BOX WITH NEW CONSTRUCTION BAR HANGER


- Box slides to any position
- Meets NEC 314.27
- Tested Max. Load: 500 Lbs.
- K.O.s sides: (4) 1/2" & 1/2" NM cable clamps
- Std. Pkg: 25



ITEM	BOX DEPTH	PRICE EACH
54171-FANBH	2-1/8"	\$9.99

4" OCTAGON FAN-RATED BOX WITH TELESCOPING "CUT-IN" BAR HANGER


- Box slides to any position
- Meets NEC 314.27
- Tested Max. Load: 500 Lbs.
- Std. Pkg: 25



1) Cut hole & insert bracket.



2) Twist out to bite on joists.



3) Install box.



ITEM	SIDE K.O.S BOTTOM K.O.S	BOX DEPTH	PRICE EACH
54171-FANOW	(4) 1/2" (2) 1/2"	2-1/8"	\$13.99

4" OCTAGON BOXES

2-1/8" Deep Bracket Boxes

1/2" K.O.S FAN-RATED WEATHERPROOF WITH BRACKET 2-1/8" DEEP



- Meets NEC 314.27
- Tested Max. Load: 500 Lbs.
- K.O.s sides: (3) 1/2"
- K.O.s bottom: (5) 1/2"
- Std. Pkg: 25

Item: 54171-FANWP

\$10.99 Each

1/2" K.O.S FAN-RATED WITH BRACKET 2-1/8" DEEP




- Meets NEC 314.27
- Tested Max. Load: 500 Lbs.
- K.O.s sides: (3) 1/2"
- K.O.s bottom: (3) 1/2", (2) 3/4"
- Std. Pkg: 25

Item: 54171-FAN

\$7.99 Each

1/2" K.O.S VERTICAL BRACKET 2-1/8" DEEP



- Side K.O.s: (3) 1/2"
- K.O.s bottom: (5) 1/2"
- 1/2" bracket setback
- Std. Pkg: 25

Item: 54171-F

\$3.49 Each

MC CABLE CLAMPS VERTICAL BRACKET 2-1/8" DEEP

- Clamps: (4) BX/MC cable
- Side K.O.s: (1) 1/2"
- Bottom K.O.s: (1) 1/2"
- 1/2" bracket setback
- Std. Pkg: 25

Item: 54171-FBX

\$3.99 Each

NM CABLE CLAMPS VERTICAL BRACKET 2-1/8" DEEP

- Clamps: (4) NM cable
- Side K.O.s: (1) 1/2"
- Bottom K.O.s: (1) 1/2"
- 1/2" bracket setback
- Std. Pkg: 25

Item: 54171-FR

\$3.79 Each

MC CABLE CLAMPS FLUSH-MOUNT BRACKET 2-1/8" DEEP


- Clamps: (4) BX/MC cable
- Side K.O.s: (2) 1/2"
- K.O.s bottom: (1) 1/2"
- Std. Pkg: 25

Item: 54171-JBX

\$3.99 Each

NM CABLE CLAMPS FLUSH-MOUNT BRACKET 2-1/8" DEEP

- Clamps: (4) NM cable
- Side K.O.s:
- K.O.s bottom:
- Std. Pkg: 25



Item: 54171-JBR

\$3.99 Each

INSTALLATION ACCESSORIES

OPEN-SPLICE ENCLOSURE WITH BRACKET 2-1/8" DEEP


- (8) side slots for insertion of NM cable open splices
- NM cable clamps, removeable side panels
- Cover included
- Std. Pkg: 25




Item: 54171-FOPR



\$7.99 Each



OPEN SPLICE



NOW TO CODE!

Also see 54171-OPR box previously, without bracket.


Box Installation Accessories

BACKSIDE DRYWALL-STANDOFF BRACKET FOR 4" WALL DEPTH

- Snaps onto box side to prevent bend-back into wall opening
- Std. Pkg: 100



Item: ABS




\$0.42 Each

BACKSIDE DRYWALL-STANDOFF BRACKET FOR 6" WALL DEPTH

- Snaps onto box side to prevent bend-back into wall opening
- Std. Pkg: 100



Item: ABS6



\$0.44 Each

GREEN GROUND SCREW

- Size/thread: 10-32
- Length: 3/8"
- Style: Combo Philips/slotted hex washer head
- Std. Pkg: 100



Item: GS

\$0.04 Each

SELF-TAPPING GREEN GROUND SCREW

- Self-drilling & tapping
- Size/thread: 10-32
- Length: 3/4"
- Style: Combo Philips/slotted hex washer head
- Std. Pkg: 100



Item: GSST

\$0.07 Each


GROUND-WIRE CLIP

- Snaps onto box edge
- Length: 1/4"
- Std. Pkg: 100



**OLD BOX EAR-TAB
CONVERSION CLIPS**

- Each clip has a 6-32 & an 8-32 threaded hole
- Std. Pkg: 100 Pairs



Install clips



Mount modern covers

Item: GC

\$0.19 Each

Item: EC

\$3.29 Pair

**GREEN GROUNDING
PIGTAILS**

- Std. Pkg: 100



FIG. 1



FIG. 2



FIG. 3



FIG. 4

ITEM	FIG	WIRE SIZE	WIRE TYPE	OVERALL LENGTH	ATTACHMENT	PRICE EACH
PTST14GN	1	14 Gauge	Stranded	8"	Flanged Spade Terminal & Captive 10-32 Green Screw	\$0.45
PTST12GN	1	12 Gauge	Stranded	8"	Flanged Spade Terminal & Captive 10-32 Green Screw	\$0.49
PTST12GN-NGS	2	12 Gauge	Stranded	8"	Flanged Spade Terminal & Prestripped 5/8"	\$0.55
PTSO14GN	3	14 Gauge	Solid	8"	Captive 10-32 Green Screw & Stripped 5/8"	\$0.36
PTSO12GN	3	12 Gauge	Solid	8"	Captive 10-32 Green Screw & Stripped 5/8"	\$0.29
PTSO12GN-S	4	12 Gauge	Solid	8"	Stripped 5/8" on both ends	\$0.41
PTSO12GN-10	3	12 Gauge	Solid	10"	Captive 10-32 Green Screw & Stripped 5/8"	\$0.45

**GOT AN INSTALL PROBLEM?
CALL US...WE CAN HELP!**

INSTALLATION ACCESSORIES

Power Leads

POWER PIGTAIL LEADS

- Overall lead length: 8"
- Std. Pkg: 100



STRANDED WIRE



SOLID WIRE



14 Gauge Stranded Wire

ITEM	COLOR	ATTACHMENT	PRICE EACH
PTST14BK	Black	Flanged Spade Terminal & Prestripped 5/8"	\$0.47
PTST14WH	White		\$0.47
PTST14RD	Red		\$0.47
PTST14YE	Yellow		\$0.47
PTST14BU	Blue		\$0.47

12 Gauge Stranded Wire

ITEM	COLOR	ATTACHMENT	PRICE EACH
PTST12BK	Black	Flanged Spade Terminal & Prestripped 5/8"	\$0.54
PTST12WH	White		\$0.54
PTST12RD	Red		\$0.54
PTST12YE	Yellow		\$0.54
PTST12BU	Blue		\$0.54

14 Gauge Solid Wire

ITEM	COLOR	ATTACHMENT	PRICE EACH
PTSO14BK	Black	Both Ends Prestripped 5/8"	\$0.39
PTSO14WH	White		\$0.39
PTSO14RD	Red		\$0.39
PTSO14YE	Yellow		\$0.39
PTSO14BU	Blue		\$0.39

12 Gauge Solid Wire


ITEM	COLOR	ATTACHMENT	PRICE EACH
PTSO12BK	Black	Both Ends Prestripped 5/8"	\$0.43
PTSO12WH	White		\$0.43
PTSO12RD	Red		\$0.43
PTSO12YE	Yellow		\$0.43
PTSO12BU	Blue		\$0.43

INSTALLATION ACCESSORIES

Knockout Seals

KNOCKOUT SEALS

- Galvanized steel




ITEM	K.O. SIZE	STD. PKG.	PRICE EACH
KOS-50	1/2"	50	\$0.49
KOS-75	3/4"	50	\$0.69
KOS-100	1"	50	\$1.39
KOS-125	1-1/4"	10	\$1.99
KOS-150	1-1/2"	10	\$2.99
KOS-200	2"	10	\$3.59
KOS-250*	2-1/2"	10	\$3.99
KOS-300*	3"	10	\$4.99
KOS-350*	3-1/2"	10	\$5.99
KOS-400*	4"	10	\$7.99
KOS-500*	5"	10	\$24.99
KOS-600*	6"	10	\$34.99

*Not UL Listed

AIR-TIGHT PLENUM KNOCKOUT SEALS

- Galvanized steel
- Gasketed



SLIDE IN FOR AIR-TIGHT SEAL.

ITEM	K.O. SIZE	STD. PKG.	PRICE EACH
KOS-50-VT	1/2"	10	\$2.99
KOS-75-VT	3/4"	10	\$3.49
KOS-100-VT	1"	10	\$4.99
KOS-125-VT	1-1/4"	5	\$5.79
KOS-150-VT	1-1/2"	5	\$6.39
KOS-200-VT	2"	5	\$7.99
KOS-250-VT*	2-1/2"	5	\$9.99
KOS-300-VT*	3"	5	\$13.99
KOS-350-VT*	3-1/2"	5	\$24.99
KOS-400-VT*	4"	5	\$27.99
KOS-500-VT*	5"	5	\$29.99
KOS-600-VT*	6"	5	\$39.99

*Not UL Listed

OIL-TIGHT KNOCKOUT SEALS

- Galvanized steel
- Gasketed




ITEM	K.O. SIZE	STD. PKG.	PRICE EACH
KOS-50-OT	1/2"	50	\$3.99
KOS-75-OT	3/4"	50	\$4.79
KOS-100-OT	1"	50	\$7.49
KOS-125-OT	1-1/4"	10	\$8.49
KOS-150-OT	1-1/2"	10	\$8.99
KOS-200-OT	2"	10	\$9.99
KOS-250-OT*	2-1/2"	10	\$10.99
KOS-300-OT*	3"	10	\$14.99
KOS-350-OT*	3-1/2"	10	\$26.99
KOS-400-OT*	4"	10	\$29.99

*Not UL Listed

STAINLESS STEEL OIL-TIGHT KNOCKOUT SEALS

- 316 Stainless steel
- Gasketed



ITEM	K.O. SIZE	STD. PKG.	PRICE EACH
KOS-50-OTSS	1/2"	50	\$12.99
KOS-75-OTSS	3/4"	50	\$14.99
KOS-100-OTSS	1"	50	\$18.99
KOS-125-OTSS	1-1/4"	10	\$19.99
KOS-150-OTSS	1-1/2"	10	\$21.99
KOS-200-OTSS	2"	10	\$26.99
KOS-250-OTSS	2-1/2"	10	\$59.99
KOS-300-OTSS	3"	10	\$69.99
KOS-350-OTSS	3-1/2"	10	\$79.99
KOS-400-OTSS	4"	10	\$89.99

INSTALLATION ACCESSORIES

Knockout Seals & Bushings

SNAP-IN KNOCKOUT SEALS

- Galvanized steel




ITEM	K.O. SIZE	STD. PKG.	PRICE EACH
SNAP50	1/2"	100	\$0.18
SNAP75	3/4"	100	\$0.27
SNAP100	1"	50	\$0.47
SNAP125	1-1/4"	50	\$0.55
SNAP150	1-1/2"	25	\$0.79
SNAP200	2"	25	\$0.95



PLASTIC KNOCKOUT INSULATING BUSHING


- Snaps in box K.O. hole
- Protects low-voltage wiring from sharp box edges



ITEM	FOR K.O. OPENING	STD. PKG.	PRICE EACH
KOB-50	1/2"	50	\$0.15
KOB-75	3/4"	50	\$0.17
KOB-100	1"	50	\$0.26
KOB-125	1-1/4"	25	\$0.29
KOB-150	1-1/2"	25	\$0.35

PLASTIC KNOCKOUT BUSHING - STAR CONFIGURATION


- Snaps in box K.O. hole
- Slits allow easy pull-through
- Protects cable from sharp box edges



ITEM	BOX K.O.	STD. PKG.	PRICE EACH
KOBS-50	1/2"	50	\$0.18
KOBS-75	3/4"	50	\$0.19

RUBBER KNOCKOUT BUSHING

- Fits: 1/2" K.O. opening
- Protects low-voltage wiring from sharp box edges
- Std. Pkg: 50




Item: KOBR-50

\$0.19 Each

"CUT-IN" BOX OLD-WORK CLIPS

- Snaps on box edge and collapses behind drywall to secure box
- Std. Pkg: 100 (50 pairs)




Item: OWC

\$0.69 Pair

"CUT-IN" BOX OLD-WORK EARS

- Screw-on ears attach at box opening to prevent box falling inside wall cavity.
- Std. Pkg: 100





Item: OWE

\$0.22 Each

KNOCKOUT REDUCING WASHERS

- Galvanized steel



3/4"

ITEM	REDUCES K.O. HOLE		STD. PKG.	PRICE EACH
	FROM	TO		
RW-7550	3/4"	1/2"	100	\$0.19

1"

ITEM	REDUCES K.O. HOLE		STD. PKG.	PRICE EACH
	FROM	TO		
RW-10050	1"	1/2"	100	\$0.29
RW-10075	1"	3/4"	100	\$0.29

1-1/4"

ITEM	REDUCES K.O. HOLE		STD. PKG.	PRICE EACH
	FROM	TO		
RW-12550	1-1/4"	1/2"	50	\$0.39
RW-12575	1-1/4"	3/4"	50	\$0.39
RW-125100	1-1/4"	1"	50	\$0.39

1-1/2"

ITEM	REDUCES K.O. HOLE		STD. PKG.	PRICE EACH
	FROM	TO		
RW-15050	1-1/2"	1/2"	50	\$0.43
RW-15075	1-1/2"	3/4"	50	\$0.43
RW-150100	1-1/2"	1"	50	\$0.43
RW-150125	1-1/2"	1-1/4"	50	\$0.43

2"

ITEM	REDUCES K.O. HOLE		STD. PKG.	PRICE EACH
	FROM	TO		
RW-20050	2"	1/2"	50	\$0.67
RW-20075	2"	3/4"	50	\$0.67
RW-200100	2"	1"	50	\$0.67
RW-200125	2"	1-1/4"	50	\$0.67
RW-200150	2"	1-1/2"	50	\$0.67

2-1/2"

ITEM	REDUCES K.O. HOLE		STD. PKG.	PRICE EACH
	FROM	TO		
RW-25050	2-1/2"	1/2"	50	\$0.89
RW-25075	2-1/2"	3/4"	50	\$0.89
RW-250100	2-1/2"	1"	50	\$0.89
RW-250125	2-1/2"	1-1/4"	50	\$0.89
RW-250150	2-1/2"	1-1/2"	50	\$0.89
RW-250200	2-1/2"	2"	50	\$0.89

3"

ITEM	REDUCES K.O. HOLE		STD. PKG.	PRICE EACH
	FROM	TO		
RW-30050	3"	1/2"	25	\$1.19
RW-30075	3"	3/4"	25	\$1.19
RW-300100	3"	1"	25	\$1.19
RW-300125	3"	1-1/4"	25	\$1.19
RW-300150	3"	1-1/2"	25	\$1.19
RW-300200	3"	2"	25	\$1.19
RW-300250	3"	2-1/2"	25	\$1.19

3-1/2"

ITEM	REDUCES K.O. HOLE		STD. PKG.	PRICE EACH
	FROM	TO		
RW-35050	3-1/2"	1/2"	25	\$3.99
RW-35075	3-1/2"	3/4"	25	\$3.99
RW-350100	3-1/2"	1"	25	\$3.99
RW-350125	3-1/2"	1-1/4"	25	\$3.99
RW-350150	3-1/2"	1-1/2"	25	\$3.99
RW-350200	3-1/2"	2"	25	\$3.99
RW-350250	3-1/2"	2-1/2"	25	\$3.99
RW-350300	3-1/2"	3"	25	\$3.99

4"

ITEM	REDUCES K.O. HOLE		STD. PKG.	PRICE EACH
	FROM	TO		
RW-40050	4"	1/2"	10	\$8.69
RW-40075	4"	3/4"	10	\$8.69
RW-400100	4"	1"	10	\$8.69
RW-400125	4"	1-1/4"	10	\$8.69
RW-400150	4"	1-1/2"	10	\$8.69
RW-400200	4"	2"	10	\$8.69
RW-400250	4"	2-1/2"	10	\$8.69
RW-400300	4"	3"	10	\$8.69
RW-400350	4"	3-1/2"	10	\$8.69

INSTALLATION ACCESSORIES

Fire Stop

FIRE-STOP EXPANSION FOAM

- Std. Pkg: 1



ITEM	SIZE	DESCRIPTION	PRICE EACH
FSFOM	12 oz.	Polyurethane, fireblocking foam sealant, easy I.D. orange, evaluated per UL ER 38112-01, type V residential fireblock. 5 mins. tack-free, 1 hour to trim. Full cure 12 - 24 hours.	\$10.69

NOTE: Federal law prohibits air freight on this item.

FIRE-STOP CAULK

10.3 OZ.


- Std. Pkg: 1



ITEM	SIZE	PRICE EACH
FSCLK10	10.3 oz.	\$7.99

FIRE-STOP PUTTY PAD

- Std. Pkg: 1



ITEM	SIZE	PRICE EACH
FSPAD	7" x 7" x 1/8"	\$4.99

DUCT SEAL PUTTY

- Std. Pkg: 1



ITEM	SIZE	PRICE EACH
DS1	1 Lb.	\$2.89
DS5	5 Lbs.	\$8.99

NOTE: DS1 & DS5 are not fire-rated.

4" SQUARE

Flat Covers

BLANK COVER

- Blank
- Std. Pkg: 50



Item: 52C1



\$0.39 Each

BLANK, RED COVER

- Blank
- Std. Pkg: 50



Item: 52C1-RED



\$1.49 Each

AIR-TIGHT PLENUM COVER

- Blank gasketed with captive 8-32 box screws
- Approved for air-plenum spaces
- Std. Pkg: 25



Item: 52C1-VT



\$2.59 Each

RED AIR-TIGHT PLENUM COVER

- Blank gasketed with captive 8-32 box screws
- Approved for air-plenum spaces
- Std. Pkg: 25



Item: 52C1-VTRED



\$3.99 Each

COVER WITH 15A TOGGLE SWITCH ASSEMBLY

- Gray toggle switch
- Std. Pkg: 25



Item: 52C1-TOG

\$4.29 Each

COVER WITH 1/2" K.O.

- 1/2" center knockout
- Std. Pkg: 50



Item: 52C6



\$0.69 Each

STAINLESS STEEL GASKETED COVER (1/2" K.O.)

- K.O.s: (1) 1/2" in center
- Std. Pkg: 50



Item: 52C6-VT-SS



\$15.99 Each

DOUBLE-GASKETED RING

- Double-gasketed
- Use with plenum extension rings
- Std. Pkg: 25



Item: 53C1-VT





\$4.69 Each

4" SQUARE


Fixture/Device Hangers

**"HANDS-FREE" SWIVEL
FIXTURE HANGER**

- Fits conduit: 1/2" or 3/4"
- Swings 20° from vertical
- Easy hands-free wiring by one installer
- Std. Pkg: 25

Item: **SC-5075HF****\$13.99** Each**SOLID SWIVEL
FIXTURE HANGERS**

- Fits conduit: 1/2" or 3/4"
- Swings 20° from vertical
- Std. Pkg: 25

Item: **SC-50** (1/2" Conduit)
Item: **SC-75** (3/4" Conduit)**\$9.99** Each**"SAFETY-GROUND"
SWIVEL FIXTURE HANGER**

- Fits conduit: 1/2" or 3/4"
- Swings 20° from vertical
- Ground wire connects pivot ball to cover
- Std. Pkg: 25

Bond wire connects
cover and pivot ballItem: **GSC-5075****\$11.99** Each**WEATHERPROOF SWIVEL
FIXTURE HANGER**

- Gasketed cover provides vapor-tight seal
- Fits conduit: 1/2" or 3/4"
- Swings 20° from vertical
- Std. Pkg: 25

Item: **SC-50-VT****\$13.99** Each

**STAINLESS STEEL
SWIVEL FIXTURE HANGER**

- Gasketed cover provides vapor-tight seal
- Fits conduit: 1/2" or 3/4"
- Swings 20° from vertical
- Std. Pkg: 25



Item: SC-50-VTSS

\$21.99 Each

**SOLID WHITE SWIVEL
FIXTURE HANGER**

- Fits conduit: 1/2" or 3/4"
- Swings 20° from vertical
- Std. Pkg: 25



Item: SC-5075WH

\$13.99 Each

**SOLID BLACK SWIVEL
FIXTURE HANGER**

- Fits conduit: 1/2" or 3/4"
- Swings 20° from vertical
- Std. Pkg: 25



Item: SC-5075BK

\$13.99 Each


CALL FOR VOLUME DISCOUNTS!
847-455-0188

4" SQUARE

One-Gang Device Rings

GALVANIZED STATIONARY FIXTURE HANGERS

- Will not swing or rotate
- Std. Pkg: 25



ITEM	CONDUIT SIZE	PRICE EACH
52C50	1/2"	\$6.99
52C75	3/4"	\$7.99
52C100	1"	\$8.29
52C125	1-1/4"	\$8.79

WHITE STATIONARY FIXTURE HANGERS


- Will not swing or rotate
- Great for cameras, occupancy sensors, horns & strobes
- Std. Pkg: 25



ITEM	CONDUIT SIZE	PRICE EACH
52C50-WH	1/2"	\$7.99
52C75-WH	3/4"	\$8.99
52C100-WH	1"	\$9.29
52C125-WH	1-1/4"	\$9.99

ADJUSTABLE-DEPTH ONE-GANG DEVICE RINGS

- Std. Pkg: 25




ITEM	ADJUSTABLE DEPTH	PRICE EACH
AMR158	5/8 to 1-1/4"	\$4.79
AMR1	3/4 to 1-1/2" Raised	\$4.79

STAINLESS STEEL ONE-GANG DEVICE RINGS

- 316 Stainless Steel



RAISED



FLAT



ITEM	RAISED	STD. PKG.	PRICE EACH
52C62A-SS	Flat	50	\$12.99
52C62-SS	1/4"	50	\$12.99
52C13-SS	1/2"	50	\$11.99
52C14-SS	5/8" or 3/4"	50	\$14.99
52C15-SS	1"	25	\$15.99
52C16-SS	1-1/4"	25	\$18.99
52C22-SS	1-1/2"	25	\$24.99
52C23-SS	2"	25	\$29.99

STEEL ONE-GANG DEVICE RINGS



ITEM	RAISED	STD. PKG.	PRICE EACH
52C62A	Flat	50	\$1.29
52C62	1/4"	50	\$0.92
52C13	1/2"	50	\$0.55
52C14-5/8	5/8"	50	\$0.55
52C14	3/4"	50	\$0.69
52C15	1"	25	\$0.99
52C16	1-1/4"	25	\$1.29
52C22	1-1/2"	25	\$2.49
52C23	2"	25	\$2.69
52C26	2-1/2"	25	\$5.99
52C28	3-1/2"	25	\$5.99

ONE-GANG TILE COVERS


- 90° square corners



ITEM	RAISED	STD. PKG.	PRICE EACH
52C13SQ	1/2"	50	\$2.19
52C14SQ	3/4"	50	\$2.29
52C15SQ	1"	25	\$2.99
52C16SQ	1-1/4"	25	\$3.99
52C22SQ	1-1/2"	25	\$5.99
52C23SQ	2"	25	\$5.99

ONE-GANG OFFSET DEVICE RINGS

- Std. Pkg: 25



- Moves device away from trim molding.



ITEM	RAISED	PRICE EACH
52C09	Flat	\$2.99
52C10	1/4"	\$2.79
52C11	1/2"	\$3.99
52C12	5/8"	\$4.49
52C12-3/4	3/4"	\$4.69
52C12-1	1"	\$4.99

4" SQUARE

One-Gang Device Covers

ONE-GANG DEVICE-RING EXTENDER

- Long 6-32 device screws included
- Std. Pkg: 25



ITEM	ACTUAL RAISED DIMENSION	PRICE EACH
DEX-150	0.56"	\$2.89
DEX-175	0.81"	\$2.99

- Raises buried device ring to finished wall surface!

LOW-VOLTAGE ONE-GANG DEVICE RINGS



VERTICAL



HORIZONTAL

ITEM	RAISED	STD. PKG.	PRICE EACH
SLR-150	1/2"	50	\$1.79
SLR-158	5/8"	25	\$1.79
SLR-175	3/4"	25	\$1.99



ONE-GANG SNAP-IN WIRE PROTECTOR SHIELD FOR STEEL DEVICE RINGS

- Protects wires during drywall install
- Snaps into one-gang steel plaster rings
- Std. Pkg: 50



Item: WPP1

\$0.47 Each

**GANGABLE DEVICE
PROTECTOR SHIELD**

- Protects toggle, duplex, decor, & GFCI devices
- Fits over pre-installed devices
- Std. Pkg: 50



Item: WPPU



\$0.39 Each

**ONE-GANG RECEPTACLE
PROTECTOR SHIELD**

- Protects duplex, decor, & GFCI devices
- Fits over pre-installed devices
- Std. Pkg: 50



Item: WPPDUP



\$0.49 Each

**ONE-GANG TOGGLE SWITCH
PROTECTOR SHIELD**

- Protects toggle, duplex, decor, & GFCI devices
- Fits over pre-installed devices
- Std. Pkg: 50



Item: WPPTOG





\$0.49 Each

4" SQUARE


Two-Gang Device Rings

ADJUSTABLE-DEPTH TWO-GANG DEVICE RING

- Telescoping ring adjusts to finished wall depth
- Std. Pkg: 25



RETRACTED
(3/4" Raised)



EXTENDED
(1-1/2" Raised)




ITEM	ADJUSTABLE DEPTH	PRICE EACH
AMR2	3/4 to 1-1/2" Raised	\$5.79

STAINLESS STEEL TWO-GANG DEVICE RINGS



RAISED



FLAT




ITEM	RAISED	STD. PKG.	PRICE EACH
52C20A-SS	Flat	50	\$14.99
52C20-SS	1/4"	50	\$14.99
52C17-SS	1/2"	50	\$14.99
52C18-SS	5/8" or 3/4"	50	\$16.99
52C19-SS	1"	25	\$17.99
52C21-SS	1-1/4"	25	\$22.99
52C24-SS	1-1/2"	25	\$26.99

TWO-GANG DEVICE RINGS



RAISED




FLAT



ITEM	RAISED	STD. PKG.	PRICE EACH
52C20A	Flat	50	\$1.19
52C20	1/4"	50	\$1.39
52C17	1/2"	50	\$0.82
52C18-5/8	5/8"	50	\$0.79
52C18	3/4"	50	\$0.89
52C19	1"	25	\$1.69
52C21	1-1/4"	25	\$1.89
52C24	1-1/2"	25	\$2.69
52C25	2"	25	\$2.99

TWO-GANG TILE COVERS

- 90° square corners




ITEM	RAISED	STD. PKG.	PRICE EACH
52C17SQ	1/2"	50	\$4.19
52C18SQ	3/4"	50	\$4.29
52C19SQ	1"	25	\$4.99
52C21SQ	1-1/4"	25	\$5.99
52C24SQ	1-1/2"	25	\$7.99
52C25SQ	2"	25	\$8.99

4" SQUARE

Two-Gang Device Rings

TWO-GANG DEVICE-RING EXTENDER



ITEM	ACTUAL RAISED DIMENSIONS	STD. PKG.	PRICE EACH
DEX-250	0.56"	25	\$3.29
DEX-275	0.81"	25	\$3.99

- Raises buried device ring to finished wall surface!

LOW-VOLTAGE TWO-GANG DEVICE RINGS



HORIZONTAL DEVICES




VERTICAL DEVICES



ITEM	RAISED	STD. PKG.	PRICE EACH
SLR-250	1/2"	50	\$1.79
SLR-258	5/8"	25	\$1.79
SLR-275	3/4"	25	\$1.99

TWO-GANG SCREW-ON PROTECTOR PLATE

- Screws into two-gang steel device rings
- Std. Pkg: 25



Item: WPP2G



Exposed wires...



PROTECTED
Ready for Drywall

\$0.99 Each

DEVICE SEPARATOR PARTITIONS

- Break-off tabs for correct fit with device ring
- Std. Pkg: 50




ITEM	FOR BOX DEPTH	FOR RAISED DEVICE RINGS	PRICE EACH
LVP41	1-1/2"	1/2", 3/4" & 1"	\$2.89
LVP42	1-1/2"	1-1/4", 1-1/2" & 2"	\$2.89
LVP41D	2-1/8"	1/2", 3/4" & 1"	\$2.99
LVP42D	2-1/8"	1-1/4", 1-1/2" & 2"	\$2.99

4" SQUARE

Square-to-Round Device Rings

SQUARE-TO-OCTAGON DEVICE RING

- Converts 4" square box to 4" octagon opening
- Extra space for LED driver
- Std. Pkg: 25



PATENT PENDING

ITEM	RAISED	PRICE EACH
52C4-5/8	5/8"	\$3.59

SQUARE-TO-ROUND ADJUSTABLE-DEPTH DEVICE RING

- Telescoping ring adjusts to finished wall depth
- Std. Pkg: 25



RETRACTED




EXTENDED



ITEM	ADJUSTABLE DEPTH	PRICE EACH
AMR0	3/4 to 1-1/2" Raised	\$5.69

SQUARE-TO-ROUND PERFECT-FIT DEVICE RINGS

- (8) Perfect-fit mounting holes
- Std. Pkg: 25



ITEM	RAISED	PRICE EACH
EXR-F	Flat	\$2.09
EXR-1/2	1/2"	\$0.99
EXR-5/8	5/8"	\$1.09
EXR-3/4	3/4"	\$1.69
EXR-1	1"	\$3.49
EXR-1-1/4	1-1/4"	\$3.09
EXR-1-1/2	1-1/2"	\$4.09
EXR-2	2"	\$4.69



GARVIN
ELECTRICAL MANUFACTURER

Got A Product Idea!

WE CAN MAKE IT



Your Dream Can Become Reality!

SQUARE-TO-ROUND DEVICE RINGS




ITEM	RAISED	STD. PKG.	PRICE EACH
52C3-F	Flat	50	\$1.59
52C3	1/2"	50	\$0.69
52C3-5/8	5/8"	50	\$0.89
52C3-3/4	3/4"	50	\$1.69
52C3-1	1"	50	\$3.39
52C3-1-1/4	1-1/4"	25	\$2.79
52C3-1-1/2	1-1/2"	25	\$3.99
52C3-2	2"	25	\$4.49



SQUARE-TO-ROUND UNIVERSAL FIXTURE RINGS

- Mounting holes 2-3/4" and 3-1/2" C.C. for any fixture
- Std. Pkg: 50



ITEM	RAISED	PRICE EACH
52C3-1/2U	1/2"	\$1.69
52C3-5/8U	5/8"	\$1.79
52C3-3/4U	3/4"	\$1.99



TOGGLE SWITCH LOCK BRACKET

- Rugged steel
- Lock-holes diameter: 0.31"
- Std. Pkg: 10



(lock not included)

ITEM	COLOR	PRICE EACH
TOGLOK	Silver	\$2.99
TOGLOKRD	Red	\$3.29
TOGLOKWH	White	\$3.29

4" SQUARE

Industrial Covers

BLANK

- Std. Pkg: 50

Item: **G1929****\$2.99** Each**STAINLESS STEEL
BLANK**

- 316 Stainless steel
- Std. Pkg: 50

Item: **G1929-SS****\$29.99** Each**DUPLEX RECEPTACLE**

- Std. Pkg: 50

Item: **G1938****\$1.39** Each**STAINLESS STEEL
DUPLEX RECEPTACLE**

- 316 Stainless steel
- Std. Pkg: 50

Item: **G1938-SS****\$29.99** Each**TWO DUPLEX
RECEPTACLE**

- Std. Pkg: 50

Item: **G1939****\$1.29** Each**STAINLESS STEEL
TWO DUPLEX
RECEPTACLE**

- 316 Stainless steel
- Std. Pkg: 50

Item: **G1939-SS****\$29.99** Each**TOGGLE SWITCH**

- Std. Pkg: 50

Item: **G1935****\$1.49** Each**STAINLESS STEEL
TOGGLE SWITCH**

- 316 Stainless steel
- Std. Pkg: 50

Item: **G1935-SS****\$29.99** Each

INDICATOR TOGGLE FOR GAS BURNER SWITCH

- Painted red
- Std. Pkg: 25



Item: BP-1935

\$3.29 Each

INDICATOR TOGGLE FOR OIL BURNER SWITCH

- Painted red
- Std. Pkg: 25



Item: BPO-1935

\$3.29 Each

TWO TOGGLE SWITCH

- Std. Pkg: 50



Item: G1936

\$1.69 Each

STAINLESS STEEL TWO TOGGLE SWITCHES

- 316 Stainless steel
- Std. Pkg: 50



Item: G1936-SS

\$29.99 Each

INDICATOR TOGGLE FOR TWO GAS BURNER SWITCHES

- Painted red
- Std. Pkg: 25



Item: BP-1936

\$3.29 Each

INDICATOR TOGGLE FOR TWO OIL BURNER SWITCHES

- Painted red
- Std. Pkg: 25



Item: BPO-1936

\$3.29 Each

DECORATIVE/GFCI RECEPTACLE

- Std. Pkg: 50



Item: G1947

\$1.99 Each

STAINLESS STEEL DECORATIVE/GFCI RECEPTACLE

- 316 Stainless steel
- Std. Pkg: 50



Item: G1947-SS

\$29.99 Each

4" SQUARE

Industrial Covers

TWO DECORATIVE OR GFCI RECEPTACLES

- Std. Pkg: 50



Item: G1950

**\$2.49** Each**STAINLESS STEEL TWO DECORATIVE OR GFCI RECEPTACLES**

- 316 Stainless steel
- Std. Pkg: 50



Item: G1950-SS

**\$29.99** Each**1/2" K.O. - CENTERED**

- Std. Pkg: 50



Item: G1930

**\$4.39** Each**SINGLE RECEPTACLE 1.406" DIAMETER**

- Std. Pkg: 50



Item: G1932

**\$1.99** Each**TWO SINGLE RECEPTACLES 1.406" DIAMETER**

- Std. Pkg: 50



Item: G1933

**\$3.99** Each**30-50A RECEPTACLE 2.141" DIAMETER**

- Std. Pkg: 50



Item: G1934

**\$3.99** Each**SINGLE RECEPTACLE 1.406" DIAMETER & TOGGLE SWITCH**

- Std. Pkg: 50



Item: G1937

**\$1.99** Each**SINGLE RECEPTACLE 1.406" DIAMETER & DUPLEX**

- Std. Pkg: 50



Item: G1940

**\$2.99** Each

4" SQUARE
Industrial Covers

DUPLEX & TOGGLE

• Std. Pkg: 50



Item: **G1941**

\$1.49 Each

**20A RECEPTACLE
1.594" DIAMETER**

• Std. Pkg: 50



Item: **G1942**

\$1.29 Each

**30A RECEPTACLE
1.719" DIAMETER**

• Std. Pkg: 50



Item: **G1943**

\$1.99 Each

**30-50A RECEPTACLE
2.141" DIAMETER**

• Std. Pkg: 50



Item: **G1944**

\$1.99 Each

**DECORATIVE/GFCI
& TOGGLE**

• Std. Pkg: 50



Item: **G1948**

\$1.59 Each

**30-60A RECEPTACLE
2.441" DIAMETER**

• Std. Pkg: 50



Item: **G1949**

\$2.49 Each

**DUPLEX &
DECORATIVE/GFCI**

• Std. Pkg: 50



Item: **G1951**

\$1.89 Each

**DECORATIVE/GFCI
& SINGLE RECEPTACLE
1.406" DIAMETER**

• Std. Pkg: 50



Item: **G1952**

\$3.99 Each

4-11/16" SQUARE

Flat Covers

BLANK COVER

- Blank cover
- Std. Pkg: 50



Item: 72C1

\$0.79 Each**BLANK RED COVER**

- Blank cover
- Std. Pkg: 50



Item: 72C1-RED

\$2.99 Each**1/2" KNOCKOUT**

- 1/2" K.O.
- Std. Pkg: 50



Item: 72C6

\$0.89 Each**STAINLESS STEEL
1/2" KNOCKOUT**

- Gasketed with centered 1/2" K.O.
- Std. Pkg: 50



Item: 72C6-VTSS

\$17.99 Each**AIR-TIGHT PLENUM COVER**

- Blank gasketed with captive 8-32 box screws
- Std. Pkg: 25



Item: 72C1-VT

\$4.99 Each**RED AIR-TIGHT
PLENUM COVER**

- Blank gasketed with captive 8-32 box screws
- Std. Pkg: 25



Item: 72C1-VTRED

\$4.99 Each**GASKETED RING**


- Double-gasketed
- Use with plenum extension rings
- Std. Pkg: 25



Item: 73C1-VT

\$6.99 Each**4-11/16" TO 4" SQUARE
CONVERSION PLATE**

- Adapts 4-11/16" boxes to accept all 4" square device rings & covers
- Std. Pkg: 50




Item: 72CP


\$5.99 Each

**"HANDS-FREE" SWIVEL
FIXTURE HANGER**

- Fits 1/2" & 3/4" conduit
- Hinged door allows hands-free wiring
- Std. Pkg: 10



SWING IN



LOCK TAB & WIRE UP



TIGHTEN DOWN

ITEM	FITS CONDUIT	PRICE EACH
SC-507511BHF	1/2" or 3/4"	\$39.99

**SOLID SWIVEL FIXTURE
HANGER**

- Fits conduit: 1/2" or 3/4"
- Std. Pkg: 10



Item: SC-507511B

\$29.99 Each

**SOLID WEATHERPROOF
SWIVEL FIXTURE HANGER**

- Gasketed cover provides vapor-tight seal
- Fits conduit: 1/2" or 3/4"
- Std. Pkg: 10



Item: SC-507511B-VT

\$35.99 Each

**STAINLESS STEEL SOLID
SWIVEL FIXTURE HANGER**

- Gasketed cover provides vapor-tight seal
- Fits conduit: 1/2" or 3/4"
- Std. Pkg: 10



Item: SC-507511B-VTSS


\$45.99 Each

4-11/16" SQUARE

Device Rings

4-11/16" TO 4" SQUARE RAISED DEVICE COVER

- Raised ring adapts 4-11/16" boxes to accept all 4" square devices
- Std. Pkg: 25



ITEM	ACTUAL 4" SQ, RAISED DIMENSION	PRICE EACH
72C4S-1/2	0.56"	\$5.99
72C4S-3/4	0.81"	\$5.99

ADJUSTABLE-DEPTH ONE-GANG DEVICE RING

- Telescoping ring adjusts 3/4" to 1-1/2"
- Std. Pkg: 10



RETRACTED
(3/4" raised)




EXTENDED
(up to 1-1/2" raised)

Item: AMR111B

\$9.99 Each

ONE-GANG DEVICE RINGS



ITEM	RAISED	STD. PKG.	PRICE EACH
72C62A	Flat	50	\$5.79
72C62	1/4"	50	\$5.79
72C13	1/2"	50	\$2.99
72C14-5/8	5/8"	50	\$2.19
72C14	3/4"	25	\$2.19
72C15	1"	25	\$1.99
72C16	1-1/4"	25	\$2.79
72C22	1-1/2"	25	\$4.99
72C23	2"	25	\$5.99

ADJUSTABLE-DEPTH TWO-GANG DEVICE RING

- Telescoping ring adjusts 3/4" to 1-1/2"
- Std. Pkg: 10



RETRACTED
(3/4" raised)



EXTENDED
(up to 1-1/2" raised)

Item: AMR211B

\$10.99 Each

TWO-GANG DEVICE RINGS



ITEM	RAISED	STD. PKG.	PRICE EACH
72C20A	Flat	50	\$4.99
72C20	1/4"	50	\$4.99
72C17	1/2"	25	\$1.39
72C18-5/8	5/8"	25	\$2.69
72C18	3/4"	25	\$2.49
72C19	1"	25	\$3.99
72C21	1-1/4"	25	\$3.99
72C24	1-1/2"	25	\$4.99
72C25	2"	25	\$5.99

DEVICE SEPARATOR PARTITIONS

- Break-off tabs for easy fitting
- Std. Pkg: 25



ITEM	DESCRIPTION	PRICE EACH
LVP51	"Slide-In" Partition for flat, 1/4", 1/2", 3/4" & 1" raised rings	\$3.99
LVP52	"Slide-In" Partition for 5/8", 1-1/4", 1-1/2" & 2" raised rings	\$3.99

SQUARE-TO-ROUND ADJUSTABLE DEPTH DEVICE RING

- Telescoping ring adjusts to finished wall depth
- Std. Pkg: 10



RETRACTED
(3/4" raised)



EXTENDED
(up to 1-1/2" raised)

ITEM	ADJUSTABLE DEPTH	PRICE EACH
AMR011B	3/4 to 1-1/2" Raised	\$9.99

CALL FOR VOLUME DISCOUNTS!
847-455-0188

4-11/16" SQUARE

Device Rings

SQUARE-TO-ROUND DEVICE RINGS


- Std. Pkg: 25



ITEM	RAISED	PRICE EACH
72C3-F	Flat	\$4.99
72C3	1/2"	\$4.99
72C3-5/8	5/8"	\$3.69
72C3-3/4	3/4"	\$3.99
72C3-1	1"	\$4.59
72C3-1-1/4	1-1/4"	\$2.79
72C3-1-1/2	1-1/2"	\$6.79
72C3-2	2"	\$6.99

SQUARE-TO-ROUND PERFECT-FIT DEVICE RINGS

- Eight mounting tabs for easy fixture alignment
- Std. Pkg: 25



ITEM	RAISED	PRICE EACH
72EXR-F	Flat	\$4.49
72EXR-1/2	1/2"	\$4.69
72EXR-5/8	5/8"	\$4.79
72EXR-3/4	3/4"	\$4.89
72EXR-1	1"	\$4.99
72EXR-1-1/4	1-1/4"	\$5.29
72EXR-1-1/2	1-1/2"	\$5.49
72EXR-2	2"	\$5.99

4-11/16" SQUARE-TO-4" OCTAGON DEVICE RINGS

- Patent Pending
- Std. Pkg: 25



ITEM	RAISED	PRICE EACH
72C4-5/8	5/8"	\$6.99

**Extra room for
LED drivers!**

BLANK

- Call for custom device holes
- Std. Pkg: 25



Item: 72C29

\$6.99 Each

**ROUND RECEPTACLE
1.406" DIAMETER**

- Std. Pkg: 25



Item: 72C32

\$5.99 Each

TOGGLE SWITCH

- Std. Pkg: 25



Item: 72C35

\$3.29 Each

TWO TOGGLE SWITCHES

- Std. Pkg: 25



Item: 72C36

\$5.99 Each

**TWO ROUND RECEPTACLES
1.406" DIAMETER**

- Std. Pkg: 25



Item: 72C37

\$5.99 Each

DUPLEX RECEPTACLE

- Std. Pkg: 25



Item: 72C38

\$5.99 Each

TWO DUPLEX RECEPTACLES

- Std. Pkg: 25



Item: 72C39

\$5.99 Each

**ROUND RECEPTACLES
1.62" DIAMETER**

- Std. Pkg: 25



Item: 72C40

\$5.99 Each

**DUPLEX RECEPTACLE
& TOGGLE SWITCH**

- Std. Pkg: 25



Item: 72C41

\$5.99 Each

**ROUND RECEPTACLE
1.594" DIAMETER**

- Std. Pkg: 25



Item: 72C42

\$7.99 Each

4-11/16" SQUARE

Industrial Covers

**30-50A ROUND RECEPTACLE
2.141" DIAMETER**

• Std. Pkg: 25



Item: 72C44

**\$5.99** Each**HUBBELL CS-6369 50 AMP
TWIST-LOCK RECEPTACLE**

• Std. Pkg: 25



Item: 72C45

**\$15.99** Each**DECORATIVE/GFCI
RECEPTACLE**

• Std. Pkg: 25



Item: 72C47

**\$11.99** Each**DECORATIVE/GFCI
& TOGGLE SWITCH**

• Std. Pkg: 25



Item: 72C48

**\$12.99** Each**TWO DECORATIVE/GFCI
RECEPTACLES**

• Std. Pkg: 25



Item: 72C49

**\$15.99** Each**30-60A ROUND RECEPTACLE
2.441" DIAMETER**

• Std. Pkg: 25



Item: 72C50

**\$5.99** Each**DUPLEX & DECORATIVE/
GFCI RECEPTACLES**

• Std. Pkg: 25





Item: 72C51

**\$15.99** Each

**YOUR PRODUCT
HERE!**



**Find out how...
847-455-0188**

BLANK COVER



ITEM	DESCRIPTION	STD. PKG.	PRICE EACH
5BC	Flat blank cover	25	\$1.79

5" SQUARE TO 4" SQUARE CONVERSION PLATE




ITEM	DESCRIPTION	STD. PKG.	PRICE EACH
5CP	Converts 5" box to accept 4" square covers	25	\$2.99

ONE-GANG DEVICE RINGS




ITEM	RAISED	STD. PKG.	PRICE EACH
5150	1/2"	25	\$3.19
5158	5/8"	25	\$3.19
5175	3/4"	25	\$3.29
51100	1"	25	\$3.59
51125	1-1/4"	25	\$3.89
51150	1-1/2"	25	\$5.99
51200	2"	25	\$5.99



ONE-GANG ADJUSTABLE-DEPTH DEVICE RINGS



ITEM	RAISED	STD. PKG.	PRICE EACH
51AMR-158	5/8" to 1-1/4"	25	\$11.99
51AMR-1	3/4" to 1-1/2"	25	\$11.99

5" SQUARE**Flat Covers & Device Rings****TWO-GANG DEVICE RINGS**



ITEM	RAISED	STD. PKG.	PRICE EACH
5250	1/2"	25	\$3.29
5258	5/8"	25	\$3.29
5275	3/4"	25	\$3.39
52100	1"	25	\$3.79
52125	1-1/4"	25	\$4.99
52150	1-1/2"	25	\$5.59
52200	2"	25	\$5.59

TWO-GANG ADJUSTABLE-DEPTH DEVICE RINGS

ITEM	RAISED	STD. PKG.	PRICE EACH
52AMR-2	3/4" to 1-1/2"	10	\$9.99

6" SQUARE-TO-4" SQUARE CONVERSION PLATE

- Adapts 6" box to accept all 4" square covers & device rings
- NEW DESIGN! Works with adjustable-depth device rings
- Std. Pkg: 25




Item: 6CP



\$3.99 Each

FLAT BLANK COVER

- Std. Pkg: 25



Item: 6BC




\$2.99 Each

ONE-GANG ADJUSTABLE-DEPTH DEVICE RING

- Telescoping ring adjusts to finished wall depth
- Std. Pkg: 10



RETRACTED



EXTENDED

ITEM	ADJUSTABLE DEPTH	PRICE EACH
61AMR-158	5/8" to 1-1/4" Raised	\$9.99
61AMR-1	3/4 to 1-1/2" Raised	\$9.99

ONE-GANG DEVICE RINGS

- Std. Pkg: 25



ITEM	RAISED	PRICE EACH
61-1/2	1/2"	\$3.59
61-5/8	5/8"	\$3.69
61-3/4	3/4"	\$3.99
61-1	1"	\$3.99
61-1-1/4	1-1/4"	\$4.29
61-1-1/2	1-1/2"	\$4.99
61-2	2"	\$4.99




6" SQUARE


Flat Covers & Device Rings

TWO-GANG ADJUSTABLE-DEPTH DEVICE RING

- Telescoping ring adjusts to finished wall depth
- Std. Pkg: 10



RETRACTED




EXTENDED

ITEM	ADJUSTABLE DEPTH	PRICE EACH
62AMR-2	3/4 to 1-1/2" Raised	\$11.99

TWO-GANG DEVICE RINGS

- Std. Pkg: 25




ITEM	RAISED	PRICE EACH
62-1/2	1/2"	\$3.79
62-5/8	5/8"	\$4.19
62-3/4	3/4"	\$3.99
62-1	1"	\$3.99
62-1-1/4	1-1/4"	\$4.29
62-1-1/2	1-1/2"	\$4.39
62-2	2"	\$4.69

THREE-GANG ADJUSTABLE-DEPTH DEVICE RING

- Telescoping ring adjusts to finished wall depth
- Std. Pkg: 10



RETRACTED



EXTENDED

ITEM	ADJUSTABLE DEPTH	PRICE EACH
63AMR-3	3/4 to 1-1/2" Raised	\$15.99


CALL FOR VOLUME DISCOUNTS!
847-455-0188

HANDY/UTILITY

Box Covers

MINI HANDY BOX BLANK COVER

- Size: 3-3/4" H x 1-1/2" W
- Captive screws
- Std. Pkg: 50



Item: G19190

\$1.29 Each

BLANK

- Includes screws
- Std. Pkg: 100



Item: G19290

\$0.29 Each

BLANK STAINLESS STEEL

- Includes screws & gasket
- Std. Pkg: 100



Item: G19290-SS

\$7.99 Each

SINGLE RECEPTACLE 1.41" DIAMETER

- Includes captive screws
- Std. Pkg: 25



Item: G19320

\$0.69 Each

TOGGLE SWITCH

- Includes captive screws
- Std. Pkg: 100



Item: G19350

\$0.59 Each

GAS BURNER TOGGLE SWITCH

- Painted red
- ON/OFF Arrows
- "EMERGENCY" indicator
- Std. Pkg: 25



Item: BP-19350

\$2.99 Each

OIL BURNER TOGGLE SWITCH

- Painted red
- ON/OFF Arrows
- "EMERGENCY" indicator
- Std. Pkg: 25



Item: BPO-19350

\$2.99 Each

DUPLEX RECEPTACLE

- Includes captive screw
- Std. Pkg: 100



Item: G19380

\$0.32 Each

COVERS & DEVICE RINGS

HANDY/UTILITY

Box Covers

0.47" DIAMETER HOLE

- Includes captive screws
- Std. Pkg: 25

Item: **G19390****\$1.29** Each**20A ROUND RECEPTACLE
1.594" DIAMETER**

- Includes captive screws
- Std. Pkg: 25

Item: **G19420****\$1.39** Each**1/2" KNOCKOUT**

- Includes captive screws
- Std. Pkg: 100

Item: **G19430****\$0.59** Each**GFCI/DECORATIVE
RECEPTACLE**

- Includes captive screws
- Std. Pkg: 100

Item: **G19470****\$0.69** Each**DUAL KNOCKOUTS**

- (1) 1/2"-3/4" concentric K.O. & (1) 1/2" open K.O. hole
- Includes captive screws
- Std. Pkg: 25

Item: **G19530****\$1.59** Each

OVERSIZED HANDY/UTILITY

Box Covers

OVERSIZED HANDY BOX COVER, BLANK

• Std. Pkg: 25



Item: G20290

\$0.89 Each

OVERSIZED HANDY BOX COVER, SINGLE RECEPTACLE 1.41" DIAMETER

• Std. Pkg: 25



Item: G20320

\$0.89 Each

OVERSIZED HANDY BOX COVER, TOGGLE SWITCH

• Std. Pkg: 25



Item: G20350

\$0.89 Each

OVERSIZED HANDY BOX COVER, DUPLEX RECEPTACLE

• Std. Pkg: 25



Item: G20380

\$0.89 Each

OVERSIZED HANDY BOX COVER, 1/2" CENTERED KNOCKOUT

• Std. Pkg: 25



Item: G20430

\$0.89 Each

OVERSIZED HANDY BOX COVER, GFCI/DECORATIVE RECEPTACLE

• Std. Pkg: 25



Item: G20470

\$0.89 Each

C
O
V
E
R
S
&
D
E
V
I
C
E
R
I
N
G
S

MULTI-GANG BOX

Device Rings

TWO-GANG


- Std. Pkg: 20



ITEM	RAISED	PRICE EACH
GBDC-122	1/2"	\$8.49
GBDC-342	3/4"	\$7.99

THREE-GANG


- Std. Pkg: 25



ITEM	RAISED	PRICE EACH
GBDC-123	1/2"	\$6.99
GBDC-343	3/4"	\$5.99

ADJUSTABLE-DEPTH THREE-GANG

- Telescoping ring adjusts to finished wall depth
- Std. Pkg: 20



RETRACTED



EXTENDED



ITEM	RAISED	PRICE EACH
AMR3	Adjustable 3/4" to 1-1/2"	\$12.99

FOUR-GANG


- Std. Pkg: 10




ITEM	RAISED	PRICE EACH
GBDC-124	1/2"	\$8.99
GBDC-344	3/4"	\$7.49

ADJUSTABLE-DEPTH FOUR-GANG

- Telescoping ring adjusts to finished wall depth
- Std. Pkg: 5



RETRACTED



EXTENDED



ITEM	RAISED	PRICE EACH
AMR4	Adjustable 3/4" to 1-1/2"	\$32.99

FIVE-GANG


- Std. Pkg: 10




ITEM	RAISED	PRICE EACH
GBDC-125	1/2"	\$17.99
GBDC-345	3/4"	\$12.99

ADJUSTABLE-DEPTH FIVE-GANG

- Telescoping ring adjusts to finished wall depth
- Std. Pkg: 5



RETRACTED



EXTENDED



ITEM	RAISED	PRICE EACH
AMR5	Adjustable 3/4" to 1-1/2"	\$39.99

SIX-GANG

- Std. Pkg: 10




ITEM	RAISED	PRICE EACH
GBDC-126	1/2"	\$26.99
GBDC-346	3/4"	\$23.99

MULTI-GANG BOX


Device Rings

ADJUSTABLE-DEPTH SIX-GANG

- Telescoping ring adjusts to finished wall depth
- Std. Pkg: 5



RETRACTED




EXTENDED



ITEM	RAISED	PRICE EACH
AMR6	Adjustable 3/4" to 1-1/2"	\$49.99

SEVEN-GANG


- Std. Pkg: 5



ITEM	RAISED	PRICE EACH
GBDC-127	1/2"	\$39.99
GBDC-347	3/4"	\$24.99

EIGHT-GANG


- Std. Pkg: 5



ITEM	RAISED	PRICE EACH
GBDC-128	1/2"	\$49.99
GBDC-348	3/4"	\$39.99

NINE-GANG

- Std. Pkg: 5



ITEM	RAISED	PRICE EACH
GBDC-129	1/2"	\$59.99
GBDC-349	3/4"	\$49.99

STEP-DOWN DEVICE RINGS

- Std. Pkg: 5



FIG. 1



FIG. 2



FIG. 3



FIG. 4



FIG. 5

1/2" Raised

ITEM	FITS BOX	DEVICE OPENINGS	FIG. #	PRICE EACH
GBSD-3150	3 Gang	1 Gang	1	\$34.99
GBSD-3250	3 Gang	2 Gang	2	\$35.99
GBSD-4150	4 Gang	1 Gang	3	\$38.99
GBSD-4250	4 Gang	2 Gang	4	\$51.99
GBSD-4350	4 Gang	3 Gang	5	\$52.99

3/4" Raised

ITEM	FITS BOX	DEVICE OPENINGS	FIG. #	PRICE EACH
GBSD-3175	3 Gang	1 Gang	1	\$34.99
GBSD-3275	3 Gang	2 Gang	2	\$36.99
GBSD-4175	4 Gang	1 Gang	3	\$50.99
GBSD-4275	4 Gang	2 Gang	4	\$52.99
GBSD-4375	4 Gang	3 Gang	5	\$53.99

MULTI-GANG BOX DEVICE PARTITIONS

- Separates power vs. low voltage
- Std. Pkg: 50




FOR FLAT COVERS



FOR RAISED RINGS

Partition slides in between devices.



ITEM	FOR BOX DEPTH	FOR RAISED COVERS	PRICE EACH
GBP-158-F	1-5/8"	Flat	\$1.99
GBP-15812	1-5/8"	1/2"	\$1.99
GBP-15834	1-5/8"	3/4"	\$1.99
GBP-212-F	2-1/2"	Flat	\$2.59
GBP-21212	2-1/2"	1/2"	\$2.59
GBP-21234	2-1/2"	3/4"	\$2.59

MULTI-GANG BOX

Device-Ring Extenders

DEVICE EXTENDERS

• Std. Pkg: 5



3 Gang



4 Gang



5 Gang



6 Gang



7 Gang



8 Gang




9 Gang

1/2" Raised

ITEM	GANGS	PRICE EACH
DEX-350	3	\$24.99
DEX-450	4	\$26.99
DEX-550	5	\$29.99
DEX-650	6	\$36.99
DEX-750	7	\$44.99
DEX-850	8	\$59.99
DEX-950	9	\$72.99

3/4" Raised

ITEM	GANGS	PRICE EACH
DEX-375	3	\$25.99
DEX-475	4	\$27.99
DEX-575	5	\$30.99
DEX-675	6	\$37.99
DEX-775	7	\$45.99
DEX-875	8	\$61.99
DEX-975	9	\$73.99




RAISES DEVICE TO FINISHED WALL SURFACE

MULTI-GANG BOX

Duplex Covers

TWO-GANG DUPLEX

• Std. Pkg: 5




Item: GBDUP-2



\$8.99 Each

THREE-GANG DUPLEX

• Std. Pkg: 5



Item: GBDUP-3



\$10.99 Each

FOUR-GANG DUPLEX

• Std. Pkg: 5




Item: GBDUP-4



\$15.99 Each

FIVE-GANG DUPLEX

• Std. Pkg: 5



Item: GBDUP-5



\$19.99 Each

SIX-GANG DUPLEX

• Std. Pkg: 1



Item: GBDUP-6



\$21.99 Each

SEVEN-GANG DUPLEX

• Std. Pkg: 1



Item: GBDUP-7



\$56.99 Each

EIGHT-GANG DUPLEX

• Std. Pkg: 1



Item: GBDUP-8



\$76.99 Each

NINE-GANG DUPLEX

• Std. Pkg: 1



Item: GBDUP-9



\$96.99 Each

MULTI-GANG BOX

Toggle Covers

TWO-GANG TOGGLE SWITCH

• Std. Pkg: 5



Item: GBTC-2

**\$8.99** Each**THREE-GANG TOGGLE SWITCH**

• Std. Pkg: 5



Item: GBTC-3

**\$10.99** Each**FOUR-GANG TOGGLE SWITCH**

• Std. Pkg: 5



Item: GBTC-4

**\$15.99** Each**FIVE-GANG TOGGLE SWITCH**


• Std. Pkg: 5



Item: GBTC-5

**\$19.99** Each**SIX-GANG TOGGLE SWITCH**


• Std. Pkg: 1



Item: GBTC-6

**\$21.99** Each**SEVEN-GANG TOGGLE SWITCH**


• Std. Pkg: 1



Item: GBTC-7

**\$56.99** Each**EIGHT-GANG TOGGLE SWITCH**


• Std. Pkg: 1



Item: GBTC-8

**\$76.99** Each**NINE-GANG TOGGLE SWITCH**

• Std. Pkg: 1



Item: GBTC-9

**\$96.99** Each

MULTI-GANG BOX

GFCI/Decor Covers

TWO-GANG GFCI/DECOR

• Std. Pkg: 5




Item: GBGFI-2



\$8.99 Each

THREE-GANG GFCI/DECOR

• Std. Pkg: 5




Item: GBGFI-3



\$10.99 Each

FOUR-GANG GFCI/DECOR

• Std. Pkg: 5




Item: GBGFI-4



\$15.99 Each

FIVE-GANG GFCI/DECOR

• Std. Pkg: 5




Item: GBGFI-5



\$19.99 Each

SIX-GANG GFCI/DECOR

• Std. Pkg: 1




Item: GBGFI-6



\$21.99 Each

SEVEN-GANG GFCI/DECOR

• Std. Pkg: 1




Item: GBGFI-7



\$56.99 Each

EIGHT-GANG GFCI/DECOR

• Std. Pkg: 1




Item: GBGFI-8



\$76.99 Each

NINE-GANG GFCI/DECOR

• Std. Pkg: 1



Item: GBGFI-9



\$96.99 Each

MULTI-GANG BOX

Blank Covers

TWO-GANG BLANK

• Std. Pkg: 5



Item: GBBC-2



\$6.99 Each

THREE-GANG BLANK

• Std. Pkg: 5




Item: GBBC-3



\$8.39 Each

FOUR-GANG BLANK

• Std. Pkg: 5




Item: GBBC-4



\$13.99 Each

FIVE-GANG BLANK

• Std. Pkg: 5



Item: GBBC-5



\$17.99 Each

SIX-GANG BLANK

• Std. Pkg: 1



Item: GBBC-6



\$19.59 Each

SEVEN-GANG BLANK

• Std. Pkg: 1




Item: GBBC-7



\$54.99 Each

EIGHT-GANG BLANK

• Std. Pkg: 1



Item: GBBC-8



\$74.99 Each

NINE-GANG BLANK

• Std. Pkg: 1



Item: GBBC-9



\$94.99 Each

OCTAGON CONCRETE BOX COVERS

• Std. Pkg: 50



CBP-3/8



CBP




CBP-VT
Gasketed



CBP-B



CBP-AP



CBP-APO



CBP-APO IN-USE

ITEM	CONDUIT K.O.S. / HUB	FEATURES	PRICE EACH
CBP	(3) 1/2" & (2) 3/4"	-----	\$1.99
CBP-B	Blank	-----	\$1.99
CBP-3/8	(2) 1/2" & (2) 3/4"	3/8" Threaded Fixture Stud	\$3.99
CBP-VT*	(3) 1/2" & (2) 3/4"	Air Plenum Gasket	\$4.99
CBP-AP*	Open Hole	Adapter Plate for 4" Octagon	\$3.99
CBP-APO*	Open Hole	Adapter Plate for 2-3/4" or 3-1/2" C.C. Holes	\$2.99



*Not UL Listed

OCTAGON/ROUND

Flat Covers

**4" OCTAGON
BLANK COVER**

- Std. Pkg: 50



Item: 54C1

\$0.49 Each**4" ROUND
BLANK COVER**

- Std. Pkg: 50



Item: 54C1-R

\$0.53 Each**4" OCTAGON
BLANK COVER**


- Std. Pkg: 50



Item: 54C1-RED

\$1.49 Each**4" OCTAGON
BLANK PLENUM
COVER**

- Pre-installed gasket creates air-tight seal
- Std. Pkg: 25



Item: 54C1-VT

\$4.99 Each**4" OCTAGON
DOUBLE-GASKETED
SEALING RING**

- Use with plenum extension rings
- Air-tight seal
- Std. Pkg: 25



Item: 55C1-VT

\$5.99 Each**4" OCTAGON
COVER WITH K.O.**

- Centered 1/2" K.O.
- Std. Pkg: 50



Item: 54C6

\$0.53 Each**4" ROUND
COVER WITH K.O.**

- Centered 1/2" K.O.
- Std. Pkg: 50



Item: 54C6-R

\$0.69 Each**STAINLESS STEEL
GASKETED COVER
1/2" KNOCKOUT**

- Centered 1/2" weather-tight K.O.
- 316 Stainless Steel
- Std. Pkg: 50



Item: 54C6-VTSS

\$14.99 Each

OCTAGON/ROUND

Device Covers

4" OCTAGON DUPLEX RECEPTACLE COVER

- Std. Pkg: 50



Item: 54C40

\$1.39 Each

4" OCTAGON SINGLE RECEPTACLE COVER (1.4" DIAMETER)

- Std. Pkg: 50



Item: 54C41

\$1.39 Each

4" ROUND INDICATOR COVER FOR OIL BURNER

- Toggle switch, On/Off
- Emergency markings
- Painted red
- Std. Pkg: 25



Item: 54CBPO

\$4.99 Each

4" ROUND TOGGLE SWITCH COVER

- Std. Pkg: 50



Item: 54C42

\$1.39 Each

4" OCTAGON-TO-4" SQUARE CONCERSION PLATE

- Converts round/octagon boxes for mounting 4S devices
- Std. Pkg: 25



Item: 52C1-OCT

\$1.59 Each

CALL FOR VOLUME DISCOUNTS!
847-455-0188


C
O
V
E
R
S
&
D
E
V
I
C
E
R
I
N
G
S

OCTAGON/ROUND

Fixture/Device Hangers

4" OCTAGON STATIONARY WHITE FIXTURE HANGERS

- Will not swing or rotate
- Std. Pkg: 25



ITEM	CONDUIT SIZE	PRICE EACH
54C50-WH	1/2"	\$7.99
54C75-WH	3/4"	\$8.99
54C100-WH	1"	\$9.29
54C125-WH	1-1/4"	\$9.99

4" OCTAGON STATIONARY GALVANIZED FIXTURE HANGERS

- Will not swing or rotate
- Std. Pkg: 25



ITEM	CONDUIT SIZE	PRICE EACH
54C50	1/2"	\$6.99
54C75	3/4"	\$7.99
54C100	1"	\$8.29
54C125	1-1/4"	\$8.99

4" ROUND "HANDS-FREE" SWIVEL FIXTURE HANGER

- Fits conduit: 1/2" or 3/4"
- Swings 20° from vertical
- Hinged door allows hands-free wiring
- Std. Pkg: 25



Item: SC-5075HFR

\$13.99 Each

4" ROUND SOLID SWIVEL FIXTURE HANGERS

- Fits conduit: 1/2" or 3/4"
- Swings 20° from vertical
- Std. Pkg: 25



Item: SC-50R (1/2" Conduit)

Item: SC-75R (3/4" Conduit)

\$9.99 Each

4" ROUND SAFETY-GROUND SWIVEL FIXTURE HANGER

- Fits conduit: 1/2" or 3/4"
- Swings 20° from vertical
- Ground wire connects pivot ball to cover
- Std. Pkg: 25



Item: GSCR-5075

\$11.99 Each

4" ROUND WEATHERPROOF SWIVEL FIXTURE HANGER

- Gasketed cover provides vapor-tight seal
- Fits conduit: 1/2" or 3/4"
- Swings 20° from vertical
- Std. Pkg: 25



Item: SC-50R-VT

\$13.99 Each

OCTAGON/ROUND

Fixture/Device Hangers

4" ROUND STAINLESS STEEL SWIVEL FIXTURE HANGER

- Gasketed cover provides vapor-tight seal
- Fits conduit: 1/2" or 3/4"
- Swings 20° from vertical
- Std. Pkg: 10



Item: **SC-50R-VTSS**

\$21.99 Each

4" ROUND WHITE SWIVEL FIXTURE HANGER

- Fits conduit: 1/2" or 3/4"
- Swings 20° from vertical
- Std. Pkg: 25




Item: **SC-5075RWH**

\$12.99 Each

4" ROUND BLACK SWIVEL FIXTURE HANGER

- Fits conduit: 1/2" or 3/4"
- Swings 20° from vertical
- Std. Pkg: 25



Item: **SC-5075RBK**

\$12.99 Each

**CALL FOR
CUSTOM COVERS!**

847-455-0188

Device Rings

4" ROUND RAISED DEVICE RINGS

- 8-32 threaded holes
- 2.75" C-C
- Std. Pkg: 25



54C3-F



54C3-RED



54C3-Raised

ITEM	RAISED	PRICE EACH
54C3-F	Flat	\$2.99
54C3	1/2"	\$1.29
54C3-RED	1/2"	\$5.99
54C3-5/8	5/8"	\$1.39
54C3-3/4	3/4"	\$4.99
54C3-1	1"	\$5.39
54C3-1-1/4	1-1/4"	\$5.59
54C3-1-1/2	1-1/2"	\$5.79
54C3-2	2"	\$5.99

4" ROUND ADJUSTABLE-DEPTH DEVICE RING

- Telescoping ring adjusts to finished wall depth
- Adjustable 3/4" to 1-1/2"
- Std. Pkg: 25



Item: **AMR-00**

\$9.99 Each



RETRACTED



EXTENDED

OCTAGON/ROUND

Ceiling Blank-up Covers

5" ROUND BLANK-UP COVER - 2.75" C-C HOLES

- Fits raised rings & 3-1/2" boxes
- Color: White
- Std. Pkg: 25



Item: **CBC-F**

\$2.99 Each

5" ROUND BLANK-UP COVER - 2.75" C-C HOLES

- Edge taper: 1/4"
- Fits raised rings & 3-1/2" boxes
- Color: White
- Std. Pkg: 25



Item: **CBC-275**

\$2.79 Each

5" ROUND BLANK-UP COVER - 3.5" C-C HOLES

- Edge taper: 1/4"
- Fits 4" round/octagon boxes
- Color: White
- Std. Pkg: 25



Item: **CBC-350**

\$2.79 Each

5" ROUND UNIVERSAL BLANK-UP COVER

- Edge taper: 1/4"
- Mounts to: All rings & boxes
- Includes mounting strap/screws
- Color: White
- Std. Pkg: 25



Item: **CBCU**

\$2.69 Each

8" ROUND CEILING-BLANK-UP COVER - 2.75" C-C HOLES

- Fits raised rings & 3-1/2" boxes
- Edge taper: 1/4"
- Color: White
- Std. Pkg: 25



Item: **CBC-275800**

\$6.99 Each

8" ROUND CEILING-BOX BLANK-UP COVER - 3.5" C-C HOLES

- Edge taper: 1/4"
- Fits 4" round/octagonboxes
- Color: White
- Std. Pkg: 25




Item: **CBC-350800**

\$6.99 Each

DECORATIVE CEILING TRIM RINGS

- Hides cuts & gouges around box edges
- Use with any box or ring
- Color: White
- Std. Pkg: 25



SLOPPY OVER-CUT



MISTAKE HIDDEN




CLEAN INSTALL

ITEM	OUTSIDE DIAMETER	PRICE EACH
CBD-800	8"	\$14.99
CBD-1200	12"	\$15.99

DECORATIVE HOLE COVER

- Covers up unused wall/ceiling holes
- Includes backing bar
- Color: White
- Std. Pkg: 25



SLIDE IN HOLE



TIGHTEN DOWN

ITEM	OUTSIDE DIAMETER	PRICE EACH
CBS-800	8"	\$9.99
CBS-1200	12"	\$16.99

RECESSED CAN LIGHT BLANK-UP COVERS

- Covers unused can lights
- Multiple springs for various can depths
- Edge taper: 1/4"
- Color: White
- Std. Pkg: 25



SCREW IN!



ATTACH SPRING!



DONE!

ITEM	OUTSIDE DIAMETER	PRICE EACH
CBC-600	6"	\$13.99
CBC-800	8"	\$16.99
CBC-1200	12"	\$19.99

CAN-LIGHT CONVERSION KIT

- Convert can lights to accept pendants
- FAST & EASY!
- Includes all mounting hardware!



ITEM	I.D. / O.D.	COLOR	STD. PKG.	PRICE EACH
CLC-800	3.75" / 8"	White	10	\$15.99



Screw on crossbar.



Mount decorative trim ring.



Wire & install pendant canopy.

EMT CONDUIT

Snap-In

SNAP-IN EMT CONNECTORS NON-INSULATED



1/2" to 2"



2-1/2" to 4"



ITEM	SIZE	STD. PKG.	PRICE EACH
SICN-50	1/2"	50	\$0.35
SICN-75	3/4"	50	\$0.47
SICN-100	1"	25	\$0.67
SICN-125	1-1/4"	25	\$1.29
SICN-150	1-1/2"	25	\$1.69
SICN-200	2"	10	\$3.25
SICN-250	2-1/2"	10	\$7.79
SICN-300	3"	5	\$10.39
SICN-350	3-1/2"	5	\$12.29
SICN-400	4"	5	\$14.09



SNAP-IN EMT COUPLINGS



1/2" to 2"



2-1/2" to 4"




ITEM	SIZE	STD. PKG.	PRICE EACH
SICP-50	1/2"	50	\$0.39
SICP-75	3/4"	50	\$0.47
SICP-100	1"	25	\$0.92
SICP-125	1-1/4"	25	\$1.53
SICP-150	1-1/2"	25	\$1.79
SICP-200	2"	10	\$3.49
SICP-250	2-1/2"	10	\$9.19
SICP-300	3"	5	\$11.99
SICP-350	3-1/2"	5	\$18.59
SICP-400	4"	5	\$19.99



SNAP-ON EMT SETSCREW CONNECTOR



SNAP ON




SET SCREW

ITEM	SIZE	STD. PKG.	PRICE EACH
SOCN-50	1/2"	50	\$0.49

**NO LOCKNUT
REQUIRED!**

STEEL EMT SETSCREW CONNECTORS

- 2-1/2" through 4" sizes have two (2) setscrews



NON-INSULATED

INSULATED



Non-Insulated

ITEM	SIZE	STD. PKG.	PRICE EACH
SSCN-50	1/2"	50	\$0.19
SSCN-75	3/4"	50	\$0.28
SSCN-100	1"	25	\$0.49
SSCN-125	1-1/4"	25	\$1.19
SSCN-150	1-1/2"	25	\$1.39
SSCN-200	2"	10	\$1.89
SSCN-250	2-1/2"	10	\$7.59
SSCN-300	3"	5	\$8.99
SSCN-350	3-1/2"	5	\$10.99
SSCN-400	4"	5	\$11.89

Insulated

ITEM	SIZE	STD. PKG.	PRICE EACH
SSCN-50I	1/2"	50	\$0.21
SSCN-75I	3/4"	50	\$0.31
SSCN-100I	1"	25	\$0.55
SSCN-125I	1-1/4"	25	\$1.69
SSCN-150I	1-1/2"	25	\$1.99
SSCN-200I	2"	10	\$2.29
SSCN-250I	2-1/2"	10	\$7.49
SSCN-300I	3"	5	\$9.99
SSCN-350I	3-1/2"	5	\$10.99
SSCN-400I	4"	5	\$11.99


STEEL EMT SETSCREW COUPLINGS

- 1-1/4" through 4" sizes have two (2) hex head setscrews



1/2" to 1"


1-1/4" to 4"



ITEM	SIZE	STD. PKG.	PRICE EACH
SSCP-50	1/2"	50	\$0.19
SSCP-75	3/4"	50	\$0.32
SSCP-100	1"	25	\$0.42
SSCP-125	1-1/4"	25	\$1.09
SSCP-150	1-1/2"	25	\$1.59
SSCP-200	2"	10	\$2.19
SSCP-250	2-1/2"	10	\$4.99
SSCP-300	3"	5	\$5.29
SSCP-350	3-1/2"	5	\$5.99
SSCP-400	4"	5	\$6.19

STEEL EMT SETSCREW SLIP COUPLINGS

- Convenient sight hole ensures perfect placement!



SLIP ON...



SLIDE OVER...



LOCK DOWN.




ITEM	SIZE	STD. PKG.	PRICE EACH
SSLP-50	1/2"	50	\$1.99
SSLP-75	3/4"	50	\$2.39
SSLP-100	1"	50	\$2.79
SSLP-125	1-1/4"	25	\$6.49
SSLP-150	1-1/2"	25	\$8.39
SSLP-200	2"	10	\$9.99
SSLP-250	2-1/2"	10	\$14.39
SSLP-300	3"	10	\$17.49
SSLP-350	3-1/2"	10	\$19.99
SSLP-400	4"	5	\$22.79

EMT CONDUIT

Setscrew


EMT SETSCREW OFFSET CONNECTORS



ITEM	SIZE	STD. PKG.	PRICE EACH
OCS-50	1/2"	10	\$1.89
OCS-75	3/4"	10	\$2.49
OCS-100	1"	10	\$5.99




EMT SETSCREW VANDAL-RESISTANT CONDUIT CAPS



Proven pipe protector!

ITEM	SIZE	STD. PKG.	PRICE EACH
CAPE50	1/2"	50	\$0.99
CAPE75	3/4"	50	\$1.19
CAPE100	1"	25	\$1.99
CAPE125	1-1/4"	25	\$2.99
CAPE150	1-1/2"	10	\$3.79
CAPE200	2"	10	\$3.99
CAPE250	2-1/2"	5	\$10.99
CAPE300	3"	5	\$12.79
CAPE350	3-1/2"	5	\$15.99
CAPE400	4"	5	\$19.99

90° EMT SETSCREW ELBOWS




E-Z Pull Cover

ITEM	SIZE	STD. PKG.	PRICE EACH
ECS-50	1/2"	10	\$3.99
ECS-75	3/4"	10	\$5.49



EMT SETSCREW PULL ELBOWS



E-Z Pull Cover



ITEM	EMT SIZE	STD. PKG.	PRICE EACH
PESS-50	1/2"	10	\$1.99
PESS-75	3/4"	5	\$2.99
PESS-100	1"	10	\$8.79
PESS-125	1-1/4"	5	\$11.49



EMT CONDUIT

Setscrew

EMT SETSCREW 90° ELBOW TO BOX





E-Z Pull Cover

ITEM	EMT SIZE	STD. PKG.	PRICE EACH
PSSB-50	1/2"	10	\$3.99
PSSB-75	3/4"	10	\$5.99
PSSB-100	1"	10	\$13.99
PSSB-125	1-1/4"	5	\$16.99



EMT-TO-FLEX COMBINATION COUPLING




Setscrew EMT/Squeeze Flex

ITEM	FLEX SIZE	TO EMT SIZE	STD. PKG.	PRICE EACH
SQZEMT-50	1/2"	1/2"	25	\$1.09
SQZEMT-75	3/4"	3/4"	25	\$2.89
SQZEMT-100	1"	1"	10	\$2.99



EMT-TO-NM CABLE COMBINATION COUPLING

• Std. Pkg: 25



ITEM	SIZE	NM CABLE TO EMT SIZE	PRICE EACH
EMTNM-38	3/8"	12-2, 12-3, 14-2, 14-3	\$0.85



Compression

STEEL EMT COMPRESSION CONNECTORS



NON-INSULATED



INSULATED



Non-Insulated

ITEM	SIZE	STD. PKG.	PRICE EACH
CCN-50	1/2"	50	\$0.21
CCN-75	3/4"	50	\$0.39
CCN-100	1"	25	\$0.69
CCN-125	1-1/4"	25	\$1.29
CCN-150	1-1/2"	10	\$1.99
CCN-200	2"	10	\$2.99
CCN-250	2-1/2"	10	\$8.49
CCN-300	3"	5	\$8.79
CCN-350	3-1/2"	5	\$13.99
CCN-400	4"	5	\$18.99

Insulated

ITEM	SIZE	STD. PKG.	PRICE EACH
CCN-50I	1/2"	50	\$0.39
CCN-75I	3/4"	50	\$0.43
CCN-100I	1"	25	\$0.79
CCN-125I	1-1/4"	25	\$1.39
CCN-150I	1-1/2"	10	\$2.39
CCN-200I	2"	10	\$3.69
CCN-250I	2-1/2"	10	\$12.99
CCN-300I	3"	5	\$13.99
CCN-350I	3-1/2"	5	\$16.99
CCN-400I	4"	5	\$21.99

EMT CONDUIT

Compression

STEEL EMT COMPRESSION COUPLINGS



ITEM	SIZE	STD. PKG.	PRICE EACH
CCP-50	1/2"	50	\$0.35
CCP-75	3/4"	50	\$0.49
CCP-100	1"	25	\$0.79
CCP-125	1-1/4"	25	\$1.49
CCP-150	1-1/2"	25	\$2.29
CCP-200	2"	10	\$2.99
CCP-250	2-1/2"	10	\$8.99
CCP-300	3"	5	\$10.99
CCP-350	3-1/2"	5	\$11.99
CCP-400	4"	5	\$15.99

STEEL EMT COMPRESSION SLIP COUPLINGS

- Convenient sight hole ensures perfect placement!



SLIP ON...



SLIDE OVER...




LOCK DOWN.



ITEM	SIZE	STD. PKG.	PRICE EACH
CSLP-50	1/2"	50	\$2.39
CSLP-75	3/4"	50	\$2.69
CSLP-100	1"	25	\$2.99
CSLP-125	1-1/4"	25	\$5.99
CSLP-150	1-1/2"	25	\$6.59
CSLP-200	2"	10	\$8.19
CSLP-250	2-1/2"	10	\$17.99
CSLP-300	3"	5	\$22.79
CSLP-350	3-1/2"	5	\$26.39
CSLP-400	4"	5	\$29.99

STEEL EMT RAIN-TIGHT COMPRESSION CONNECTORS




ITEM	SIZE	STD. PKG.	PRICE EACH
CCNR-50	1/2"	50	\$0.85
CCNR-75	3/4"	50	\$0.99
CCNR-100	1"	25	\$1.09
CCNR-125	1-1/4"	25	\$2.99
CCNR-150	1-1/2"	25	\$4.39
CCNR-200	2"	10	\$5.99
CCNR-250	2-1/2"	10	\$17.99
CCNR-300	3"	5	\$26.99
CCNR-350	3-1/2"	5	\$31.99
CCNR-400	4"	5	\$39.99

STEEL EMT RAIN-TIGHT COMPRESSION COUPLINGS



ITEM	SIZE	STD. PKG.	PRICE EACH
CCPR-50	1/2"	50	\$0.79
CCPR-75	3/4"	50	\$1.29
CCPR-100	1"	25	\$1.59
CCPR-125	1-1/4"	25	\$2.99
CCPR-150	1-1/2"	25	\$3.99
CCPR-200	2"	10	\$4.99
CCPR-250	2-1/2"	10	\$21.99
CCPR-300	3"	5	\$27.99
CCPR-350	3-1/2"	5	\$29.99
CCPR-400	4"	5	\$39.99


EMT COMPRESSION OFFSET CONNECTORS




ITEM	SIZE	STD. PKG.	PRICE EACH
OCC-50	1/2"	10	\$2.49
OCC-75	3/4"	10	\$3.79



EMT TWO-PIECE CONNECTORS



SLIDE ON!




TIGHTEN DOWN!

ITEM	SIZE	STD. PKG.	PRICE EACH
TPC-50	1/2"	50	\$1.39
TPC-75	3/4"	50	\$1.49
TPC-100	1"	50	\$2.59



RIGID-TO-EMT COMBINATION COUPLING




Threaded Rigid/Compression EMT

ITEM	RIGID SIZE	EMT SIZE	STD. PKG.	PRICE EACH
RTE50	1/2"	1/2"	25	\$2.99
RTE75	3/4"	3/4"	25	\$4.99
RTE100	1"	1"	25	\$8.99
RTE125	1-1/4"	1-1/4"	25	\$14.99



90° EMT SHORT-RADIUS COMPRESSION CONNECTORS



ITEM	SIZE	STD. PKG.	PRICE EACH
EMS5090	1/2"	25	\$3.39
EMS7590	3/4"	25	\$3.59
EMS10090	1"	25	\$5.99



EMT CONDUIT

Bushings

FLAT FLOOR CONDUIT PLUG

- Plugs & protects conduit
- Eliminates dangerous “stub-up” conduit trip hazards
- Snug fit won't fall out when walked on




Push in



Safely walk on job site!

ITEM	FITS EMT	STD. PKG.	PRICE EACH
FFCP-50	1/2"	50	\$1.29
FFCP-75	3/4"	50	\$1.39
FFCP-100	1"	25	\$1.59

PLASTIC EMT INSULATING BUSHINGS



Solid bang-on



ITEM	SIZE	STD. PKG.	PRICE EACH
IB-50	1/2"	50	\$0.13
IB-75	3/4"	50	\$0.17
IB-100	1"	25	\$0.45
IB-125	1-1/4"	25	\$0.59
IB-150	1-1/2"	25	\$0.89
IB-200	2"	25	\$1.49
IB-250	2-1/2"	10	\$2.99
IB-300	3"	10	\$3.89
IB-350	3-1/2"	5	\$3.99
IB-400	4"	5	\$5.19

SPLIT PLASTIC EMT INSULATING BUSHINGS



Wraps around existing cables!

ITEM	SIZE	STD. PKG.	PRICE EACH
IBS-50	1/2"	50	\$0.49
IBS-75	3/4"	50	\$0.59
IBS-100	1"	25	\$0.99
IBS-125	1-1/4"	25	\$1.09
IBS-150	1-1/2"	25	\$1.49
IBS-200	2"	25	\$2.29
IBS-250	2-1/2"	10	\$2.99
IBS-300	3"	10	\$3.99
IBS-350	3-1/2"	5	\$4.89
IBS-400	4"	5	\$5.69

90° EMT CONDUIT ELBOWS



ITEM	SIZE	STD. PKG.	PRICE EACH
EMT-5090	1/2"	50	\$2.59
EMT-7590	3/4"	50	\$3.49
EMT-10090	1"	20	\$3.99
EMT-12590	1-1/4"	20	\$4.99
EMT-15090	1-1/2"	15	\$6.19
EMT-20090	2"	10	\$8.69
EMT-25090	2-1/2"	5	\$13.99
EMT-30090	3"	1	\$18.99
EMT-35090	3-1/2"	1	\$30.99
EMT-40090	4"	1	\$36.99



45° EMT CONDUIT ELBOWS



ITEM	SIZE	STD. PKG.	PRICE EACH
EMT-5045	1/2"	50	\$2.59
EMT-7545	3/4"	50	\$3.49
EMT-10045	1"	20	\$3.99
EMT-12545	1-1/4"	20	\$4.99
EMT-15045	1-1/2"	15	\$6.19
EMT-20045	2"	10	\$8.69
EMT-25045	2-1/2"	5	\$13.99
EMT-30045	3"	1	\$18.99
EMT-35045	3-1/2"	1	\$30.99
EMT-40045	4"	1	\$36.99




FITTINGS

GARVIN
ELECTRICAL MANUFACTURER

Need A Special Part Made?

WE CUSTOMIZE

Boxes & Covers | Fittings | Hangers & Clamps




Fast Solutions... Designed By You!

RIGID CONDUIT

Setscrew


RIGID SETSCREW CONNECTORS

- 2-1/2" through 6" sizes have two (2) setscrews



ITEM	SIZE	MATERIAL	STD. PKG.	PRICE EACH
RS-50	1/2"	Mal. Iron	25	\$3.49
RS-75	3/4"	Mal. Iron	25	\$4.49
RS-100	1"	Mal. Iron	10	\$4.99
RS-125	1-1/4"	Mal. Iron	10	\$10.99
RS-150	1-1/2"	Mal. Iron	10	\$14.99
RS-200	2"	Mal. Iron	10	\$21.99
RS-250	2-1/2"	Steel	5	\$39.99
RS-300	3"	Steel	5	\$59.99
RS-350	3-1/2"	Steel	5	\$89.99
RS-400	4"	Steel	5	\$119.99
RS-500	5"	Mal. Iron	5	\$169.99
RS-600	6"	Mal. Iron	5	\$199.99

RIGID SETSCREW COUPLINGS



ITEM	SIZE	STD. PKG.	PRICE EACH
RSC-50	1/2"	25	\$2.49
RSC-75	3/4"	25	\$3.09
RSC-100	1"	10	\$4.69
RSC-125	1-1/4"	10	\$5.69
RSC-150	1-1/2"	5	\$7.29
RSC-200	2"	5	\$16.99

VANDAL-RESISTANT RIGID CONDUIT CAPS



1/2" TO 4" STYLE



5" & 6" STYLE



Proven pipe protector

ITEM	SIZE	STD. PKG.	PRICE EACH
CAPR50	1/2"	50	\$1.79
CAPR75	3/4"	50	\$2.49
CAPR100	1"	25	\$2.89
CAPR125	1-1/4"	25	\$4.89
CAPR150	1-1/2"	10	\$6.29
CAPR200	2"	10	\$6.99
CAPE250	2-1/2"	5	\$10.99
CAPE300	3"	5	\$12.79
CAPE350	3-1/2"	5	\$15.99
CAPE400	4"	5	\$19.99
CAPR500	5"	1	\$43.99
CAPR600	6"	1	\$54.99

90° COMBINATION THREADED/ SETSCREW PULL ELBOWS




ITEM	RIGID SIZE	CONNECTION	STD. PKG.	PRICE EACH
PEC-50	1/2"	Rigid / Rigid	25	\$2.59
PEC-75	3/4"	Rigid / Rigid	10	\$3.59
PEC-100	1"	Rigid / Rigid	10	\$5.59
PEC-125	1-1/4"	Rigid / Rigid	5	\$12.99

RIGID CONDUIT

Compression


90° COMBINATION THREADED/ SETScrew PULL ELBOW TO BOX



ITEM	RIGID SIZE	CONNECTION	STD. PKG.	PRICE EACH
PECB-50	1/2"	Rigid / Box	25	\$3.19
PECB-75	3/4"	Rigid / Box	10	\$4.39
PECB-100	1"	Rigid / Box	10	\$12.99
PECB-125	1-1/4"	Rigid / Box	5	\$17.99




RIGID COMPRESSION CONNECTORS



ITEM	SIZE	STD. PKG.	PRICE EACH
RT50	1/2"	25	\$2.59
RT75	3/4"	25	\$3.89
RT100	1"	25	\$5.99
RT125	1-1/4"	10	\$7.89
RT150	1-1/2"	5	\$10.49
RT200	2"	5	\$25.99
RT250	2-1/2"	5	\$49.99
RT300	3"	5	\$59.99
RT350	3-1/2"	5	\$79.99
RT400	4"	5	\$99.99



RIGID COMPRESSION COUPLINGS




ITEM	SIZE	STD. PKG.	PRICE EACH
RTC50	1/2"	25	\$4.99
RTC75	3/4"	25	\$6.99
RTC100	1"	10	\$10.99
RTC125	1-1/4"	10	\$13.99
RTC150	1-1/2"	10	\$18.99
RTC200	2"	10	\$27.99
RTC250	2-1/2"	5	\$49.99
RTC300	3"	5	\$99.99
RTC350	3-1/2"	5	\$119.99
RTC400	4"	5	\$134.99



RIGID-TO-EMT COMBINATION COUPLING

• Std. Pkg: 25



ITEM	RIGID SIZE	EMT SIZE	PRICE EACH
RTE50	1/2"	1/2"	\$2.99
RTE75	3/4"	3/4"	\$4.99
RTE100	1"	1"	\$8.99
RTE125	1-1/4"	1-1/4"	\$14.99




FITTINGS

RIGID CONDUIT

Box Spacers/Floor Flanges

BOX SPACER CONNECTORS


- Locknuts included



ITEM	FITS K.O. SIZE	GAP LENGTH	STD. PKG.	PRICE EACH
BB-1/2	1/2"	0.20"	100	\$1.29
BB-3/4	3/4"	0.20"	50	\$2.99



PREFAB BRACKET BOX SPACER CONNECTOR



ITEM	FITS K.O. SIZE	GAP LENGTH	STD. PKG.	PRICE EACH
BB-1/2-1	1/2"	0.20"	100	\$2.59

FASTEST CONNECTION FOR CADDY® & B-LINE® WALL BRACKETS!

EXTRA-LONG BOX SPACER CONNECTOR



ITEM	FITS K.O. SIZE	BODY LENGTH	STD. PKG.	PRICE EACH
BB-1/2-2	1/2"	2"	50	\$2.99



HEAVY-DUTY FLOOR/CEILING FLANGES

- Malleable iron



ITEM	SIZE	STD. PKG.	PRICE EACH
FF50	1/2"	25	\$4.39
FF75	3/4"	25	\$5.09
FF100	1"	25	\$5.49
FF125	1-1/4"	25	\$7.29
FF150	1-1/2"	25	\$8.29
FF200	2"	25	\$10.99
FF250	2-1/2"	5	\$87.99
FF300	3"	5	\$106.99
FF400	4"	5	\$144.99
FF500	5"	1	\$225.99
FF600	6"	1	\$239.99

LIGHT-DUTY FLOOR/CEILING FLANGES

- Stamped steel



ITEM	SIZE	STD. PKG.	PRICE EACH
FFE50	1/2"	50	\$2.29
FFE75	3/4"	50	\$2.59

RIGID CONDUIT

Threaded Couplings


STAINLESS STEEL THREADED RIGID COUPLINGS

- 316 Stainless Steel



ITEM	SIZE	STD. PKG.	PRICE EACH
RC-50SS	1/2"	100	\$9.99
RC-75SS	3/4"	100	\$12.99
RC-100SS	1"	50	\$24.99
RC-125SS	1-1/4"	50	\$29.99
RC-150SS	1-1/2"	25	\$34.99
RC-200SS	2"	25	\$52.99
RC-250SS	2-1/2"	10	\$67.99
RC-300SS	3"	1	\$79.99
RC-350SS	3-1/2"	1	\$119.99
RC-400SS	4"	1	\$139.99

THREADED RIGID COUPLINGS



ITEM	SIZE	STD. PKG.	PRICE EACH
RC-50	1/2"	100	\$0.99
RC-75	3/4"	100	\$1.79
RC-100	1"	50	\$1.99
RC-125	1-1/4"	50	\$4.99
RC-150	1-1/2"	25	\$5.49
RC-200	2"	25	\$8.99
RC-250	2-1/2"	25	\$9.99
RC-300	3"	10	\$11.99
RC-350	3-1/2"	10	\$15.99
RC-400	4"	10	\$19.99
RC-500	5"	1	\$36.99
RC-600	6"	1	\$69.99

SHORT THREADED RIGID COUPLINGS




Fits ERICO/B-LINE Multi-Box Brackets

ITEM	FOR PIPE SIZE	OVERALL LENGTH	STD. PKG.	PRICE EACH
HC50	1/2"	.81"	50	\$1.09
HC75	3/4"	.82"	50	\$1.69
HC100	1"	.98"	25	\$2.19

RIGID THREE-PIECE COUPLINGS

- Malleable iron



ITEM	SIZE	STD. PKG.	PRICE EACH
3PC50	1/2"	25	\$2.29
3PC75	3/4"	25	\$3.89
3PC100	1"	20	\$5.99
3PC125	1-1/4"	20	\$11.99
3PC150	1-1/2"	10	\$13.99
3PC200	2"	10	\$21.99
3PC250	2-1/2"	2	\$84.99
3PC300	3"	2	\$110.99
3PC350	3-1/2"	1	\$169.99
3PC400	4"	1	\$179.99
3PC500	5"	1	\$229.99
3PC600	6"	1	\$269.99

RIGID CONDUIT

Concrete Slab/Deck

CONCRETE SLAB THREADED CONDUIT INSERTS - STRAIGHT



ITEM	SIZE	NATERIAL	STD. PKG.	PRICE EACH
EF50	1/2"	Cast Iron	10	\$5.99
EF75	3/4"	Cast Iron	10	\$6.99
EF100	1"	Cast Iron	10	\$7.99
EF125*	1-1/4"	Cast Iron	10	\$11.99

*Not UL Listed

Rubber gasket protects conduit threads



CONCRETE SLAB THREADED CONDUIT INSERTS - 90°



ITEM	SIZE	NATERIAL	STD. PKG.	PRICE EACH
EFL50	1/2"	Cast Iron	10	\$9.99
EFL75	3/4"	Cast Iron	10	\$11.99
EFL100	1"	Cast Iron	10	\$13.99
EFL125*	1-1/4"	Cast Metal	10	\$15.99

*Not UL Listed

Rubber gasket protects conduit threads



FLAT FLOOR CONDUIT PLUG

- Plugs & protects conduit
- Eliminates dangerous "stub-up" conduit trip hazards
- Snug fit won't fall out when walked on



Push in



Safely walk on job site!

ITEM	FITS EMT	COLOR	STD. PKG.	PRICE EACH
FFCP-50	1/2"	Blue	50	\$1.29
FFCP-75	3/4"	Orange	50	\$1.39
FFCP-100	1"	Black	25	\$1.59

EASILY POPS OUT FOR QUICK CONNECTION

RIGID CONDUIT

Threaded Insulating Bushings

CONDUIT BUSHING STEEL PENNIES



Use with threaded bushing to protect conduit raceway


ITEM	SIZE	STD. PKG.	PRICE EACH
PNY50	1/2"	50	\$0.29
PNY75	3/4"	50	\$0.39
PNY100	1"	25	\$0.89
PNY125	1-1/4"	25	\$1.29
PNY150	1-1/2"	25	\$2.19
PNY200	2"	25	\$2.59
PNY250	2-1/2"	10	\$3.69
PNY300	3"	10	\$4.69
PNY350	3-1/2"	5	\$7.99
PNY400	4"	5	\$8.99
PNY500	5"	5	\$9.99
PNY600	6"	5	\$14.99

THREADED SOLID PLASTIC INSULATING BUSHINGS



ITEM	SIZE	STD. PKG.	PRICE EACH
IBT-50	1/2"	100	\$0.14
IBT-75	3/4"	100	\$0.18
IBT-100	1"	50	\$0.35
IBT-125	1-1/4"	50	\$0.45
IBT-150	1-1/2"	50	\$0.69
IBT-200	2"	10	\$1.49
IBT-250	2-1/2"	10	\$3.09
IBT-300	3"	10	\$3.99
IBT-350	3-1/2"	10	\$5.99
IBT-400	4"	10	\$7.99
IBT-500	5"	10	\$9.99
IBT-600	6"	10	\$12.99

THREADED SPLIT PLASTIC INSULATING BUSHINGS



Installs before or after wire pull

ITEM	SIZE	STD. PKG.	PRICE EACH
IBTS-50	1/2"	50	\$0.32
IBTS-75	3/4"	50	\$0.37
IBTS-100	1"	25	\$0.51
IBTS-125	1-1/4"	25	\$0.57
IBTS-150	1-1/2"	25	\$0.83
IBTS-200	2"	25	\$1.42
IBTS-250	2-1/2"	10	\$2.19
IBTS-300	3"	10	\$2.63
IBTS-350	3-1/2"	10	\$4.13
IBTS-400	4"	10	\$5.05
IBTS-500	5"	10	\$16.49
IBTS-600	6"	10	\$19.79



Need A Special Part Made?

WE CUSTOMIZE

Boxes & Covers | Fittings | Hangers & Clamps




Fast Solutions... Designed By You!

RIGID CONDUIT

Water-Tight Hubs

STAINLESS STEEL WATER-TIGHT THREADED HUBS


- 316 Stainless Steel



ITEM	SIZE	STD. PKG.	PRICE EACH
WH50-SS	1/2"	25	\$59.99
WH75-SS	3/4"	10	\$79.99
WH100-SS	1"	10	\$99.99
WH125-SS	1-1/4"	10	\$115.99
WH150-SS	1-1/2"	10	\$139.99
WH200-SS	2"	10	\$159.99
WH250-SS	2-1/2"	5	\$199.99
WH300-SS	3"	5	\$229.99
WH350-SS	3-1/2"	5	\$259.99
WH400-SS	4"	5	\$299.99

WATER-TIGHT THREADED HUBS


- Cast metal



ITEM	SIZE	STD. PKG.	PRICE EACH
WH50	1/2"	25	\$2.99
WH75	3/4"	10	\$3.99
WH100	1"	10	\$6.29
WH125	1-1/4"	10	\$6.99
WH150	1-1/2"	10	\$8.99
WH200	2"	10	\$9.99
WH250	2-1/2"	5	\$19.99
WH300	3"	5	\$29.99
WH350	3-1/2"	5	\$34.99
WH400	4"	5	\$49.99

WATER-TIGHT HUBS WITH GROUNDING PROVISION

- Cast metal



ITEM	SIZE	MIN. WIRE SIZE	MAX. WIRE SIZE	STD. PKG.	PRICE EACH
WHG50	1/2"	#14	#1/0	25	\$9.99
WHG75	3/4"	#14	#1/0	10	\$11.99
WHG100	1"	#14	#1/0	10	\$14.99
WHG125	1-1/4"	#14	#1/0	10	\$16.99
WHG150	1-1/2"	#14	#1/0	10	\$19.99
WHG200	2"	#14	#1/0	5	\$22.99
WHG250	2-1/2"	#8	#1/0	5	\$29.99
WHG300	3"	#8	#1/0	5	\$46.99
WHG350	3-1/2"	#8	#3/0	5	\$59.99
WHG400	4"	#8	#3/0	5	\$69.99

CALL FOR VOLUME DISCOUNTS!
847-455-0188

RIGID CONDUIT

Reducing Bushings

STAINLESS STEEL REDUCING BUSHINGS



Machined
316
Stainless
Steel

1/2"

ITEM	EXTERNAL THREADS	INTERNAL THREADS	STD. PKG.	PRICE EACH
RB-5038-SS	1/2"	3/8"	100	\$44.99

1"

ITEM	EXTERNAL THREADS	INTERNAL THREADS	STD. PKG.	PRICE EACH
RB-10050-SS	1"	1/2"	50	\$26.99
RB-10075-SS	1"	3/4"	50	\$26.99

1-1/2"

ITEM	EXTERNAL THREADS	INTERNAL THREADS	STD. PKG.	PRICE EACH
RB-15050-SS	1-1/2"	1/2"	10	\$43.99
RB-15075-SS	1-1/2"	3/4"	10	\$43.99
RB-150100-SS	1-1/2"	1"	10	\$43.99
RB-150125-SS	1-1/2"	1-1/4"	10	\$43.99

2-1/2"

ITEM	EXTERNAL THREADS	INTERNAL THREADS	STD. PKG.	PRICE EACH
RB-25050-SS	2-1/2"	1/2"	5	\$189.99
RB-25075-SS	2-1/2"	3/4"	5	\$189.99
RB-250100-SS	2-1/2"	1"	5	\$189.99
RB-250125-SS	2-1/2"	1-1/4"	5	\$189.99
RB-250150-SS	2-1/2"	1-1/2"	5	\$189.99
RB-250200-SS	2-1/2"	2"	5	\$189.99

3-1/2"

ITEM	EXTERNAL THREADS	INTERNAL THREADS	STD. PKG.	PRICE EACH
RB-350200-SS	3-1/2"	2"	1	\$339.99
RB-350250-SS	3-1/2"	2-1/2"	1	\$339.99
RB-350300-SS	3-1/2"	3"	1	\$339.99

5"

ITEM	EXTERNAL THREADS	INTERNAL THREADS	STD. PKG.	PRICE EACH
RB-500400-SS	5"	4"	1	\$699.99

3/4"

ITEM	EXTERNAL THREADS	INTERNAL THREADS	STD. PKG.	PRICE EACH
RB-7550-SS	3/4"	1/2"	50	\$24.99

1-1/4"

ITEM	EXTERNAL THREADS	INTERNAL THREADS	STD. PKG.	PRICE EACH
RB-12550-SS	1-1/4"	1/2"	20	\$37.99
RB-12575-SS	1-1/4"	3/4"	20	\$37.99
RB-125100-SS	1-1/4"	1"	20	\$37.99

2"

ITEM	EXTERNAL THREADS	INTERNAL THREADS	STD. PKG.	PRICE EACH
RB-20050-SS	2"	1/2"	10	\$79.99
RB-20075-SS	2"	3/4"	10	\$79.99
RB-200100-SS	2"	1"	10	\$79.99
RB-200125-SS	2"	1-1/4"	10	\$79.99
RB-200150-SS	2"	1-1/2"	10	\$79.99

3"

ITEM	EXTERNAL THREADS	INTERNAL THREADS	STD. PKG.	PRICE EACH
RB-300100-SS	3"	1"	1	\$299.99
RB-300125-SS	3"	1-1/4"	1	\$299.99
RB-300150-SS	3"	1-1/2"	1	\$299.99
RB-300200-SS	3"	2"	1	\$299.99
RB-300250-SS	3"	2-1/2"	1	\$299.99

4"

ITEM	EXTERNAL THREADS	INTERNAL THREADS	STD. PKG.	PRICE EACH
RB-400200-SS	4"	2"	1	\$599.99
RB-400250-SS	4"	2-1/2"	1	\$599.99
RB-400300-SS	4"	3"	1	\$599.99
RB-400350-SS	4"	3-1/2"	1	\$599.99

6"

ITEM	EXTERNAL THREADS	INTERNAL THREADS	STD. PKG.	PRICE EACH
RB-600500-SS	6"	5"	1	\$899.99

STEEL REDUCING BUSHINGS



1/2"

ITEM	EXTERNAL THREADS	INTERNAL THREADS	STD. PKG.	PRICE EACH
RB-5038	1/2"	3/8"	100	\$1.29

3/4"

ITEM	EXTERNAL THREADS	INTERNAL THREADS	STD. PKG.	PRICE EACH
RB-7550	3/4"	1/2"	50	\$0.59

1"

ITEM	EXTERNAL THREADS	INTERNAL THREADS	STD. PKG.	PRICE EACH
RB-10050	1"	1/2"	50	\$0.99
RB-10075	1"	3/4"	50	\$0.99

1-1/4"

ITEM	EXTERNAL THREADS	INTERNAL THREADS	STD. PKG.	PRICE EACH
RB-12550	1-1/4"	1/2"	20	\$2.49
RB-12575	1-1/4"	3/4"	20	\$2.49
RB-125100	1-1/4"	1"	20	\$2.49



Machined Steel Zinc Plated

1-1/2"

ITEM	EXTERNAL THREADS	INTERNAL THREADS	STD. PKG.	PRICE EACH
RB-15050	1-1/2"	1/2"	10	\$3.39
RB-15075	1-1/2"	3/4"	10	\$3.39
RB-150100	1-1/2"	1"	10	\$3.39
RB-150125	1-1/2"	1-1/4"	10	\$3.39

2"

ITEM	EXTERNAL THREADS	INTERNAL THREADS	STD. PKG.	PRICE EACH
RB-20050	2"	1/2"	10	\$4.99
RB-20075	2"	3/4"	10	\$4.99
RB-200100	2"	1"	10	\$4.99
RB-200125	2"	1-1/4"	10	\$4.99
RB-200150	2"	1-1/2"	10	\$4.99

2-1/2"

ITEM	EXTERNAL THREADS	INTERNAL THREADS	STD. PKG.	PRICE EACH
RB-25050	2-1/2"	1/2"	5	\$12.99
RB-25075	2-1/2"	3/4"	5	\$12.99
RB-250100	2-1/2"	1"	5	\$12.99
RB-250125	2-1/2"	1-1/4"	5	\$12.99
RB-250150	2-1/2"	1-1/2"	5	\$12.99
RB-250200	2-1/2"	2"	5	\$12.99

3"

ITEM	EXTERNAL THREADS	INTERNAL THREADS	STD. PKG.	PRICE EACH
RB-300100	3"	1"	1	\$19.99
RB-300125	3"	1-1/4"	1	\$19.99
RB-300150	3"	1-1/2"	1	\$19.99
RB-300200	3"	2"	1	\$19.99
RB-300250	3"	2-1/2"	1	\$19.99

3-1/2"

ITEM	EXTERNAL THREADS	INTERNAL THREADS	STD. PKG.	PRICE EACH
RB-350200	3-1/2"	2"	1	\$26.99
RB-350250	3-1/2"	2-1/2"	1	\$26.99
RB-350300	3-1/2"	3"	1	\$26.99

4"

ITEM	EXTERNAL THREADS	INTERNAL THREADS	STD. PKG.	PRICE EACH
RB-400200	4"	2"	1	\$32.99
RB-400250	4"	2-1/2"	1	\$32.99
RB-400300	4"	3"	1	\$32.99
RB-400350	4"	3-1/2"	1	\$32.99

5"

ITEM	EXTERNAL THREADS	INTERNAL THREADS	STD. PKG.	PRICE EACH
RB-500400	5"	4"	1	\$79.99

6"

ITEM	EXTERNAL THREADS	INTERNAL THREADS	STD. PKG.	PRICE EACH
RB-600500	6"	5"	1	\$89.99

FITTINGS

RIGID CONDUIT

Elbows & Nipples


THREADED CONDUIT HOLE PLUGS



NO-SLIP square-head driver to tighten

ITEM	SIZE	STD. PKG.	PRICE EACH
PLG50	1/2"	50	\$1.79
PLG75	3/4"	50	\$1.99
PLG100	1"	25	\$2.69
PLG125	1-1/4"	25	\$2.99
PLG150	1-1/2"	25	\$3.69
PLG200	2"	25	\$5.99
PLG250	2-1/2"	2	\$8.99
PLG300	3"	2	\$13.99
PLG350	3-1/2"	1	\$29.99
PLG400	4"	1	\$32.99

THREADED CONDUIT ENLARGER/ REDUCER COUPLING



ITEM	CONNECTS CONDUIT		STD. PKG.	PRICE EACH
	MALE SIZE	TO FEMALE SIZE		
E5075	1/2"	3/4"	10	\$3.99
E75100	3/4"	1"	10	\$6.99
E100125	1"	1-1/4"	10	\$11.99
E125150	1-1/4"	1-1/2"	10	\$14.99

OFFSET CONDUIT NIPPLES



ITEM	SIZE	STD. PKG.	PRICE EACH
OCN50	1/2"	100	\$1.99
OCN75	3/4"	100	\$2.49
OCN100	1"	50	\$2.99
OCN125	1-1/4"	50	\$3.99
OCN150	1-1/2"	50	\$5.99
OCN200	2"	10	\$7.39
OCN250	2-1/2"	10	\$35.99
OCN300	3"	10	\$45.99
OCN350	3-1/2"	5	\$169.99
OCN400	4"	5	\$189.99

90° THREADED PULL ELBOWS



ITEM	RIGID SIZE	CONNECTION	STD. PKG.	PRICE EACH
PE-50	1/2"	Rigid / Rigid	10	\$2.39
PE-75	3/4"	Rigid / Rigid	10	\$2.99
PE-100	1"	Rigid / Rigid	10	\$7.99
PE-125	1-1/4"	Rigid / Rigid	5	\$12.99

90° THREADED PULL ELBOW TO BOX



ITEM	RIGID SIZE	CONNECTION	STD. PKG.	PRICE EACH
PEB-50	1/2"	Rigid / Box	10	\$3.79
PEB-75	3/4"	Rigid / Box	10	\$5.79
PEB-100	1"	Rigid / Box	10	\$14.99
PEB-125	1-1/4"	Rigid / Box	5	\$16.99

RIGID CONDUIT

Elbows & Nipples

THREADED BUSHED NIPPLES





Insulated throat protects wires.



ITEM	SIZE	MATERIAL	STD. PKG.	PRICE EACH
CHN-50I	1/2"	Cast Metal	100	\$0.49
CHN-75I	3/4"		50	\$0.79
CHN-100I	1"		25	\$1.39
CHN-125I	1-1/4"		25	\$2.99
CHN-150I	1-1/2"		25	\$3.29
CHN-200I	2"		25	\$4.79
CHN-250I	2-1/2"	Malleable Iron	10	\$7.99
CHN-300I	3"		10	\$9.99
CHN-350I	3-1/2"		5	\$22.99
CHN-400I	4"		5	\$29.99
CHN-500I	5"		5	\$89.99
CHN-600I	6"		5	\$99.99

STAINLESS STEEL THREADED BUSHED NIPPLES


- 316 Stainless Steel



ITEM	SIZE	STD. PKG.	PRICE EACH
CHN50-SS	1/2"	100	\$18.59
CHN75-SS	3/4"	50	\$21.39
CHN100-SS	1"	25	\$22.99
CHN125-SS	1-1/4"	25	\$24.99
CHN150-SS	1-1/2"	25	\$29.99
CHN200-SS	2"	25	\$34.99
CHN250-SS	2-1/2"	10	\$49.99
CHN300-SS	3"	10	\$66.99
CHN350-SS	3-1/2"	5	\$89.99
CHN400-SS	4"	5	\$121.99


EXTRA-LONG THREADED BUSHED NIPPLES

- Std. Pkg: 25



ITEM	SIZE	OVERALL LENGTH	PRICE EACH
CHN-50100	1/2"	1"	\$0.65
CHN-75100	3/4"	1"	\$0.85
CHN-100100	1"	1"	\$1.49

RIGID-TO-FLEXIBLE METAL CONDUIT COMBINATION COUPLING



ITEM	RIGID SIZE	FLEX SIZE	STD. PKG.	PRICE EACH
RTF50	1/2"	1/2"	25	\$2.09
RTF75	3/4"	3/4"	25	\$2.99
RTF100	1"	1"	10	\$3.89
RTF125	1-1/4"	1-1/4"	10	\$5.99

RIGID CONDUIT

Service Entrance

CLAMP-ON SERVICE ENTRANCE CAPS



ITEM	SIZE	STD. PKG.	PRICE EACH
SEC50	1/2"	15	\$3.59
SEC75	3/4"	10	\$3.99
SEC100	1"	7	\$4.99
SEC125	1-1/4"	5	\$5.69
SEC150	1-1/2"	5	\$7.99
SEC200	2"	1	\$9.99
SEC250	2-1/2"	1	\$29.99
SEC300	3"	1	\$46.99
SEC350	3-1/2"	1	\$63.99
SEC400	4"	1	\$73.99




FITTINGS

GARVIN
ELECTRICAL MANUFACTURER

Need A Special Part Made?

WE CUSTOMIZE

Boxes & Covers | Fittings | Hangers & Clamps



Fast Solutions... Designed By You!

THREADED RIGID CONDUIT NIPPLES

1/2"

ITEM	LENGTH	STD. PKG.	PRICE EACH
RN50C	Close	25	\$0.89
RN50150	1-1/2"	25	\$0.99
RN50200	2"	25	\$1.19
RN50300	3"	25	\$1.29
RN50400	4"	25	\$1.39
RN50500	5"	25	\$1.43
RN50600	6"	25	\$1.49
RN50800	8"	25	\$3.69
RN501000	10"	25	\$3.99
RN501200	12"	25	\$4.69



RN SERIES



RN SERIES CLOSE



CALL FOR CUSTOM SIZES!

3/4"

ITEM	LENGTH	STD. PKG.	PRICE EACH
RN75C	Close	25	\$1.09
RN75150	1-1/2"	25	\$1.29
RN75200	2"	25	\$1.35
RN75300	3"	25	\$1.59
RN75400	4"	25	\$1.79
RN75500	5"	25	\$1.89
RN75600	6"	25	\$1.99
RN75800	8"	25	\$3.99
RN751000	10"	25	\$4.89
RN751200	12"	25	\$5.39

1"

ITEM	LENGTH	STD. PKG.	PRICE EACH
RN100C	Close	25	\$1.69
RN100200	2"	25	\$1.89
RN100300	3"	25	\$1.99
RN100400	4"	25	\$2.39
RN100500	5"	25	\$2.69
RN100600	6"	25	\$2.89
RN100800	8"	25	\$4.99
RN1001000	10"	25	\$6.39
RN1001200	12"	25	\$7.29

1-1/4"

ITEM	LENGTH	STD. PKG.	PRICE EACH
RN125C	Close	25	\$2.09
RN125200	2"	25	\$2.19
RN125300	3"	25	\$2.59
RN125400	4"	25	\$3.09
RN125500	5"	25	\$3.29
RN125600	6"	25	\$3.49
RN125800	8"	25	\$6.69
RN1251000	10"	25	\$8.49
RN1251200	12"	25	\$9.99

1-1/2"

ITEM	LENGTH	STD. PKG.	PRICE EACH
RN150C	Close	25	\$2.59
RN150200	2"	25	\$2.69
RN150300	3"	25	\$3.29
RN150400	4"	25	\$3.99
RN150500	5"	25	\$4.59
RN150600	6"	25	\$4.79
RN150800	8"	25	\$8.39
RN1501000	10"	25	\$9.99
RN1501200	12"	25	\$10.99

2"

ITEM	LENGTH	STD. PKG.	PRICE EACH
RN200C	Close	25	\$3.09
RN200300	3"	25	\$3.99
RN200400	4"	25	\$4.99
RN200500	5"	25	\$5.99
RN200600	6"	25	\$6.89
RN200800	8"	12	\$9.99
RN2001000	10"	10	\$11.99
RN2001200	12"	10	\$13.49

2-1/2"

ITEM	LENGTH	STD. PKG.	PRICE EACH
RN250C	Close	10	\$5.89
RN250300	3"	10	\$6.49
RN250400	4"	10	\$7.69
RN250500	5"	10	\$9.29
RN250600	6"	10	\$10.39
RN250800	8"	10	\$13.19
RN2501000	10"	5	\$15.69
RN2501200	12"	5	\$17.19

3"

ITEM	LENGTH	STD. PKG.	PRICE EACH
RN300C	Close	10	\$6.99
RN300300	3"	10	\$7.49
RN300400	4"	10	\$9.19
RN300500	5"	10	\$10.99
RN300600	6"	10	\$12.19
RN300800	8"	5	\$15.69
RN3001000	10"	5	\$18.49
RN3001200	12"	1	\$22.49

3-1/2"

ITEM	LENGTH	STD. PKG.	PRICE EACH
RN350C	Close	10	\$8.49
RN350400	4"	6	\$10.99
RN350500	5"	5	\$12.99
RN350600	6"	3	\$13.99
RN350800	8"	3	\$17.49
RN3501000	10"	3	\$20.39
RN3501200	12"	1	\$23.99

4"

ITEM	LENGTH	STD. PKG.	PRICE EACH
RN400C	Close	10	\$9.99
RN400400	4"	6	\$11.99
RN400500	5"	5	\$14.49
RN400600	6"	5	\$15.49
RN400800	8"	3	\$19.99
RN4001000	10"	3	\$23.99
RN4001200	12"	1	\$28.99

RIGID CONDUIT

Elbows & Nipples

90° THREADED RIGID CONDUIT NIPPLES



ITEM	SIZE	STD. PKG.	PRICE EACH
RE-5090	1/2"	50	\$3.49
RE-7590	3/4"	50	\$4.49
RE-10090	1"	20	\$5.99
RE-12590	1-1/4"	20	\$8.99
RE-15090	1-1/2"	20	\$9.99
RE-20090	2"	10	\$18.99
RE-25090	2-1/2"	1	\$26.99
RE-30090	3"	1	\$39.99
RE-35090	3-1/2"	1	\$63.99
RE-40090	4"	1	\$79.99
RE-50090	5"	1	\$299.00
RE-60090	6"	1	\$399.00

45° THREADED RIGID CONDUIT NIPPLES



ITEM	SIZE	STD. PKG.	PRICE EACH
RE-5045	1/2"	50	\$3.49
RE-7545	3/4"	50	\$4.49
RE-10045	1"	20	\$5.99
RE-12545	1-1/4"	20	\$8.99
RE-15045	1-1/2"	20	\$9.99
RE-20045	2"	10	\$18.99
RE-25045	2-1/2"	1	\$26.99
RE-30045	3"	1	\$39.99
RE-35045	3-1/2"	1	\$63.99
RE-40045	4"	1	\$79.99

NEED A CUSTOM FITTING?

Call 847-455-0188

RIGID CONDUIT

Locknuts


STEEL LOCKNUTS



Teeth bite metal surface for secure install!

ITEM	SIZE	STD. PKG.	PRICE EACH
LN-38	3/8"	100	\$0.33
LN-50	1/2"	100	\$0.15
LN-75	3/4"	100	\$0.19
LN-100	1"	50	\$0.29
LN-125	1-1/4"	50	\$0.39
LN-150	1-1/2"	25	\$0.49
LN-200	2"	10	\$0.89
LN-250	2-1/2"	10	\$1.49
LN-300	3"	10	\$2.79
LN-350	3-1/2"	5	\$2.99
LN-400	4"	5	\$3.99
LN-500	5"	5	\$25.99
LN-600	6"	5	\$29.99

STEEL GROUNDING LOCKNUTS




E-Z Ground Screw!

ITEM	SIZE	STD. PKG.	PRICE EACH
LNG-50	1/2"	100	\$1.09
LNG-75	3/4"	100	\$1.19
LNG-100	1"	50	\$1.89
LNG-125	1-1/4"	50	\$1.99
LNG-150	1-1/2"	25	\$2.49
LNG-200	2"	25	\$3.99
LNG-250	2-1/2"	10	\$4.99
LNG-300	3"	10	\$10.99
LNG-350	3-1/2"	5	\$11.99
LNG-400	4"	5	\$13.99
LNG-500	5"	5	\$59.99
LNG-600	6"	5	\$79.99



STEEL SEALING LOCKNUTS



Built-in sealing gasket

ITEM	SIZE	STD. PKG.	PRICE EACH
LNS-50	1/2"	50	\$0.69
LNS-75	3/4"	50	\$0.89
LNS-100	1"	25	\$1.29
LNS-125	1-1/4"	10	\$1.89
LNS-150	1-1/2"	10	\$2.89
LNS-200	2"	5	\$3.99
LNS-250	2-1/2"	5	\$5.99
LNS-300	3"	5	\$9.99
LNS-350	3-1/2"	5	\$11.99
LNS-400	4"	5	\$12.99
LNS-500*	5"	5	\$49.99
LNS-600*	6"	5	\$69.99



*Not UL Listed

STAINLESS STEEL LOCKNUTS

- 316 Stainless Steel




ITEM	SIZE	STD. PKG.	PRICE EACH
LNSS-50	1/2"	100	\$1.59
LNSS-75	3/4"	100	\$1.99
LNSS-100	1"	50	\$3.39
LNSS-125	1-1/4"	50	\$4.59
LNSS-150	1-1/2"	25	\$7.99
LNSS-200	2"	10	\$11.99

RIGID CONDUIT

Grounding Bushings

SPLIT-COLLAR GROUNDING BUSHINGS





Installs before or after wire pull

ITEM	SIZE	STD. PKG.	PRICE EACH
SGB50	1/2"	50	\$19.49
SGB75	3/4"	25	\$21.99
SGB100	1"	25	\$23.99
SGB125	1-1/4"	25	\$28.99
SGB150	1-1/2"	25	\$33.99
SGB200	2"	25	\$37.99
SGB250	2-1/2"	10	\$45.99
SGB300	3"	10	\$66.99
SGB350	3-1/2"	10	\$78.99
SGB400	4"	10	\$87.99
SGB500	5"	10	\$136.99
SGB600	6"	10	\$154.99

U.L. LISTED SPLIT-COLLAR GROUNDING BUSHINGS

- Includes 4-14 AL wire lug



ITEM	SIZE	STD. PKG.	PRICE EACH
GCHK50	1/2"	50	\$19.49
GCHK75	3/4"	25	\$21.99
GCHK100	1"	25	\$23.99
GCHK125	1-1/4"	25	\$28.99
GCHK150	1-1/2"	25	\$33.99
GCHK200	2"	25	\$37.99
GCHK250	2-1/2"	10	\$45.99
GCHK300	3"	10	\$66.99
GCHK350	3-1/2"	10	\$78.99
GCHK400	4"	10	\$87.99
GCHK500	5"	10	\$136.99
GCHK600	6"	10	\$154.99

UNIVERSAL GROUNDING BUSHINGS

- Malleable iron body



ITEM	SIZE	MIN. WIRE SIZE	MAX. WIRE SIZE	STD. PKG.	PRICE EACH
UGB-50	1/2"	#14	#4	25	\$1.99
UGB-75	3/4"	#14	#4	25	\$2.39
UGB-100	1"	#14	#4	25	\$2.99
UGB-125	1-1/4"	#14	#1/0	10	\$4.99
UGB-150	1-1/2"	#14	#1/0	10	\$5.39
UGB-200	2"	#14	#1/0	10	\$6.49
UGB-250	2-1/2"	#6	#250	5	\$8.99
UGB-300	3"	#6	#250	5	\$9.99
UGB-350	3-1/2"	#6	#250	5	\$12.99
UGB-400	4"	#6	#250	5	\$14.99
UGB-500	5"	#6	250 MCM	1	\$64.99
UGB-600	6"	#6	250 MCM	1	\$84.99


CALL FOR DIFFERENT LUG SIZES

RIGID CONDUIT BODIES

Aluminum & Iron

ALUMINUM MOGUL LB CONDUIT BODIES

- Complete unit cover & gasket



STANDARD

ITEM	SIZE	STD. PKG.	PRICE EACH
MOLB-100	1"	2	\$38.99
MOLB-125	1-1/4"	2	\$22.99
MOLB-150	1-1/2"	1	\$43.99
MOLB-200	2"	1	\$59.99
MOLB-250	2-1/2"	1	\$155.99
MOLB-300	3"	1	\$169.99
MOLB-350	3-1/2"	1	\$199.99
MOLB-400	4"	1	\$239.99



TAMPER PROOF

ITEM	SIZE	STD. PKG.	PRICE EACH
MOLT-100	1"	2	\$49.99
MOLT-125	1-1/4"	2	\$35.99
MOLT-150	1-1/2"	1	\$65.99
MOLT-200	2"	1	\$69.99
MOLT-250	2-1/2"	1	\$169.99
MOLT-300	3"	1	\$185.99
MOLT-350	3-1/2"	1	\$225.99
MOLT-400	4"	1	\$259.99

ALUMINUM LB CONDUIT BODIES

- Complete unit cover & gasket



ITEM	SIZE	STD. PKG.	PRICE EACH
LB50	1/2"	10	\$3.49
LB75	3/4"	10	\$4.79
LB100	1"	5	\$6.99
LB125	1-1/4"	2	\$8.69
LB150	1-1/2"	2	\$11.99
LB200	2"	1	\$16.99
LB250	2-1/2"	1	\$49.99
LB300	3"	1	\$69.99
LB350	3-1/2"	1	\$119.99
LB400	4"	1	\$136.99



ALUMINUM SERVICE ENTRANCE LB CONDUIT BODIES

- Complete unit cover & gasket



ITEM	SIZE	STD. PKG.	PRICE EACH
SLB50	1/2"	20	\$3.89
SLB75	3/4"	20	\$5.99
SLB100	1"	10	\$7.69
SLB125	1-1/4"	5	\$9.79
SLB150	1-1/2"	5	\$12.99
SLB200	2"	3	\$18.99



RIGID CONDUIT BODIES

Aluminum & Iron

MALLEABLE IRON LB CONDUIT BODIES

- Complete unit cover & gasket



ITEM	SIZE	STD. PKG.	PRICE EACH
MLB50	1/2"	1	\$6.99
MLB75	3/4"	1	\$7.99
MLB100	1"	1	\$11.99
MLB125	1-1/4"	1	\$19.99
MLB150	1-1/2"	1	\$23.99
MLB200	2"	1	\$36.99
MLB250	2-1/2"	1	\$74.99
MLB300	3"	1	\$104.99
MLB350	3-1/2"	1	\$159.99
MLB400	4"	1	\$179.99

ALUMINUM LL CONDUIT BODIES


- Complete unit cover & gasket



ITEM	SIZE	STD. PKG.	PRICE EACH
LL50	1/2"	10	\$3.49
LL75	3/4"	10	\$4.79
LL100	1"	5	\$6.99
LL125	1-1/4"	2	\$8.49
LL150	1-1/2"	2	\$11.49
LL200	2"	1	\$16.99
LL250	2-1/2"	1	\$49.99
LL300	3"	1	\$69.99
LL350	3-1/2"	1	\$119.99
LL400	4"	1	\$136.99

MALLEABLE IRON LL CONDUIT BODIES


- Complete unit cover & gasket



ITEM	SIZE	STD. PKG.	PRICE EACH
MLL50	1/2"	1	\$6.99
MLL75	3/4"	1	\$7.99
MLL100	1"	1	\$11.99
MLL125	1-1/4"	1	\$19.99
MLL150	1-1/2"	1	\$23.99
MLL200	2"	1	\$36.99
MLL250	2-1/2"	1	\$74.99
MLL300	3"	1	\$104.99
MLL350	3-1/2"	1	\$159.99
MLL400	4"	1	\$179.99

ALUMINUM LR CONDUIT BODIES

- Complete unit cover & gasket




ITEM	SIZE	STD. PKG.	PRICE EACH
LR50	1/2"	10	\$3.49
LR75	3/4"	10	\$4.79
LR100	1"	5	\$6.99
LR125	1-1/4"	5	\$8.49
LR150	1-1/2"	5	\$11.49
LR200	2"	2	\$16.99
LR250	2-1/2"	2	\$49.99
LR300	3"	1	\$69.99
LR350	3-1/2"	1	\$119.99
LR400	4"	1	\$136.99

RIGID CONDUIT BODIES

Aluminum & Iron

MALLEABLE IRON LR CONDUIT BODIES

- Complete unit cover & gasket



ITEM	SIZE	STD. PKG.	PRICE EACH
MLR50	1/2"	1	\$6.99
MLR75	3/4"	1	\$7.99
MLR100	1"	1	\$11.99
MLR125	1-1/4"	1	\$19.99
MLR150	1-1/2"	1	\$23.99
MLR200	2"	1	\$36.99
MLR250	2-1/2"	1	\$74.99
MLR300	3"	1	\$104.99
MLR350	3-1/2"	1	\$159.99
MLR400	4"	1	\$179.99



ALUMINUM T CONDUIT BODIES

- Complete unit cover & gasket



ITEM	SIZE	STD. PKG.	PRICE EACH
LT50	1/2"	10	\$3.49
LT75	3/4"	10	\$4.79
LT100	1"	5	\$6.99
LT125	1-1/4"	5	\$8.49
LT150	1-1/2"	5	\$11.49
LT200	2"	2	\$16.99
LT250	2-1/2"	2	\$49.99
LT300	3"	1	\$69.99
LT350	3-1/2"	1	\$119.99
LT400	4"	1	\$136.99



MALLEABLE IRON T CONDUIT BODIES

- Complete unit cover & gasket



ITEM	SIZE	STD. PKG.	PRICE EACH
MT50	1/2"	1	\$6.99
MT75	3/4"	1	\$7.99
MT100	1"	1	\$11.99
MT125	1-1/4"	1	\$19.99
MT150	1-1/2"	1	\$23.99
MT200	2"	1	\$36.99
MT250	2-1/2"	1	\$74.99
MT300	3"	1	\$104.99
MT350	3-1/2"	1	\$159.99
MT400	4"	1	\$179.99



ALUMINUM C CONDUIT BODIES

- Complete unit cover & gasket



ITEM	SIZE	STD. PKG.	PRICE EACH
LC50	1/2"	10	\$3.49
LC75	3/4"	10	\$4.79
LC100	1"	5	\$6.99
LC125	1-1/4"	2	\$8.49
LC150	1-1/2"	2	\$11.49
LC200	2"	1	\$16.99
LC250	2-1/2"	1	\$49.99
LC300	3"	1	\$69.99
LC350	3-1/2"	1	\$119.99
LC400	4"	1	\$136.99



RIGID CONDUIT BODIES

Aluminum & Iron

MALLEABLE IRON C CONDUIT BODIES


- Complete unit cover & gasket



ITEM	SIZE	STD. PKG.	PRICE EACH
MC50	1/2"	1	\$6.99
MC75	3/4"	1	\$7.99
MC100	1"	1	\$11.99
MC125	1-1/4"	1	\$19.99
MC150	1-1/2"	1	\$23.99
MC200	2"	1	\$36.99
MC250	2-1/2"	1	\$74.99
MC300	3"	1	\$104.99
MC350	3-1/2"	1	\$159.99
MC400	4"	1	\$179.99

MALLEABLE IRON X CONDUIT BODIES

- Complete unit cover & gasket




ITEM	SIZE	STD. PKG.	PRICE EACH
MX1CG	1/2"	10	\$21.99
MX2CG	3/4"	10	\$24.99
MX3CG	1"	5	\$38.99
MX4CG	1-1/4"	5	\$54.99
MX5CG	1-1/2"	5	\$69.99
MX6CG	2"	2	\$119.99



Need A Special Part Made?

WE CUSTOMIZE

Boxes & Covers | Fittings | Hangers & Clamps




Fast Solutions... Designed By You!

LIQUID-TIGHT CONDUIT

Straight Connectors

PVC STRAIGHT LIQUID-TIGHT CONNECTORS



ITEM	SIZE	STD. PKG.	PRICE EACH
NMLT-38	3/8"	20	\$1.19
NMLT-50	1/2"	20	\$1.09
NMLT-75	3/4"	20	\$1.59
NMLT-100	1"	10	\$2.89
NMLT-125	1-1/4"	10	\$4.19
NMLT-150	1-1/2"	5	\$4.99
NMLT-200	2"	5	\$8.49

STAINLESS STEEL STRAIGHT LIQUID-TIGHT CONNECTORS



ITEM	SIZE	STD. PKG.	PRICE EACH
LTCSS-38	3/8"	20	\$37.99
LTCSS-50	1/2"	20	\$39.99
LTCSS-75	3/4"	10	\$46.99
LTCSS-100	1"	5	\$59.99
LTCSS-125	1-1/4"	5	\$69.99
LTCSS-150	1-1/2"	5	\$99.99
LTCSS-200	2"	5	\$149.99

STRAIGHT LIQUID-TIGHT CONNECTORS

- Malleable iron




ITEM	SIZE	STD. PKG.	PRICE EACH
LTC-38	3/8"	20	\$1.69
LTC-50	1/2"	20	\$1.73
LTC-75	3/4"	10	\$2.29
LTC-100	1"	5	\$3.99
LTC-125	1-1/4"	5	\$6.69
LTC-150	1-1/2"	5	\$8.99
LTC-200	2"	5	\$15.99
LTC-250	2-1/2"	5	\$46.99
LTC-300	3"	5	\$69.99
LTC-350	3-1/2"	5	\$89.99
LTC-400	4"	5	\$99.99
LTC-500*	5"	1	\$249.00
LTC-600*	6"	1	\$469.00

*Not UL Listed

STRAIGHT, GROUNDING LIQUID-TIGHT CONNECTORS

- Malleable iron



ITEM	SIZE	MIN. WIRE SIZE	MAX. WIRE SIZE	STD. PKG.	PRICE EACH
GLTC-38	3/8"	#14	#4	25	\$4.99
GLTC-50	1/2"	#14	#4	25	\$4.99
GLTC-75	3/4"	#14	#4	10	\$5.99
GLTC-100	1"	#14	#4	5	\$7.49
GLTC-125	1-1/4"	#14	#4	5	\$14.99
GLTC-150	1-1/2"	#14	#4	5	\$17.99
GLTC-200	2"	#14	#4	5	\$23.99
GLTC-250	2-1/2"	#8	#1/0	5	\$73.99
GLTC-300	3"	#8	#1/0	5	\$109.99
GLTC-350	3-1/2"	#8	#3/0	5	\$133.99
GLTC-400	4"	#8	#3/0	5	\$149.99
GLTC-500	5"	#8	#250MCM	5	\$289.00
GLTC-600	6"	#8	#250MCM	5	\$599.00

LIQUID-TIGHT CONDUIT

90° Connectors

PVC 90° LIQUID-TIGHT CONNECTORS



ITEM	SIZE	STD. PKG.	PRICE EACH
NMLT-3890	3/8"	20	\$1.89
NMLT-5090	1/2"	20	\$1.89
NMLT-7590	3/4"	20	\$2.89
NMLT-10090	1"	10	\$3.99
NMLT-12590	1-1/4"	10	\$8.99
NMLT-15090	1-1/2"	10	\$9.99
NMLT-20090	2"	10	\$11.99

STAINLESS STEEL 90° LIQUID-TIGHT CONNECTORS



ITEM	SIZE	STD. PKG.	PRICE EACH
LTCSS-5090	1/2"	20	\$59.99
LTCSS-7590	3/4"	20	\$69.99
LTCSS-10090	1"	5	\$89.99
LTCSS-12590	1-1/4"	5	\$139.99
LTCSS-15090	1-1/2"	5	\$169.99
LTCSS-20090	2"	5	\$239.99

90° LIQUID-TIGHT CONNECTORS


- Malleable iron



ITEM	SIZE	STD. PKG.	PRICE EACH
LTC-3890	3/8"	20	\$2.59
LTC-5090	1/2"	20	\$2.39
LTC-7590	3/4"	20	\$3.99
LTC-10090	1"	5	\$6.99
LTC-12590	1-1/4"	5	\$11.99
LTC-15090	1-1/2"	5	\$14.99
LTC-20090	2"	5	\$19.99
LTC-25090	2-1/2"	5	\$69.99
LTC-30090	3"	5	\$89.99
LTC-35090	3-1/2"	5	\$109.99
LTC-40090	4"	5	\$129.99

90° GROUNDING LIQUID-TIGHT CONNECTORS

- Malleable iron



ITEM	SIZE	GROUND WIRE		STD. PKG.	PRICE EACH
		MIN. SIZE	MAX. SIZE		
GLTC-3890	3/8"	#14	#4	25	\$7.99
GLTC-5090	1/2"	#14	#4	25	\$7.99
GLTC-7590	3/4"	#14	#4	10	\$8.99
GLTC-10090	1"	#14	#4	10	\$9.99
GLTC-12590	1-1/4"	#14	#4	5	\$16.99
GLTC-15090	1-1/2"	#14	#4	2	\$19.99
GLTC-20090	2"	#14	#4	1	\$26.99
GLTC-25090	2-1/2"	#8	#1/0	1	\$82.99
GLTC-30090	3"	#8	#1/0	1	\$124.99
GLTC-35090	3-1/2"	#8	#3/0	1	\$159.99
GLTC-40090	4"	#8	#3/0	1	\$173.99


FITTINGS

LIQUID-TIGHT CONDUIT

45° Connectors

45° LIQUID-TIGHT CONNECTORS


- Malleable iron



ITEM	SIZE	STD. PKG.	PRICE EACH
LTC-3845	3/8"	20	\$2.59
LTC-5045	1/2"	20	\$2.39
LTC-7545	3/4"	10	\$3.99
LTC-10045	1"	5	\$6.99
LTC-12545	1-1/4"	5	\$11.99
LTC-15045	1-1/2"	5	\$14.99
LTC-20045	2"	5	\$19.99
LTC-25045	2-1/2"	5	\$69.99
LTC-30045	3"	5	\$89.99
LTC-35045	3-1/2"	5	\$109.99
LTC-40045	4"	5	\$129.99

45° GROUNDING LIQUID-TIGHT CONNECTORS

- Malleable iron



ITEM	SIZE	GROUND WIRE		STD. PKG.	PRICE EACH
		MIN. SIZE	MAX. SIZE		
GLTC-3845	3/8"	#14	#4	25	\$7.99
GLTC-5045	1/2"	#14	#4	25	\$7.99
GLTC-7545	3/4"	#14	#4	10	\$8.99
GLTC-10045	1"	#14	#4	10	\$9.99
GLTC-12545	1-1/4"	#14	#4	5	\$16.99
GLTC-15045	1-1/2"	#14	#4	2	\$19.99
GLTC-20045	2"	#14	#4	1	\$26.99
GLTC-25045	2-1/2"	#8	#1/0	1	\$82.99
GLTC-30045	3"	#8	#1/0	1	\$124.99
GLTC-35045	3-1/2"	#8	#3/0	1	\$159.99
GLTC-40045	4"	#8	#3/0	1	\$173.99


FITTINGS

GARVIN
ELECTRICAL MANUFACTURER

Need A Special Part Made?

WE CUSTOMIZE

Boxes & Covers | Fittings | Hangers & Clamps




Fast Solutions... Designed By You!

MC CABLE

Snap-In

SNAP-IN MC CABLE CONNECTOR

- Snap-in cable, NO TOOLS required
- Fits 14/3 & 10/2 cable
- Std. Pkg: 50



Item: EZ143102



SNAP IN CABLE...




SNAP ON BOX!



\$0.69 Each

DOUBLE-SNAP STRAIGHT "CUT-IN" CONNECTOR

- Std. Pkg: 50



SNAP IN CABLE...




SNAP ON BOX!

ITEM	SIZE	PRICE EACH
DSL38	3/8"	\$0.69



DOUBLE-SNAP STRAIGHT CONNECTOR

- Std. Pkg: 50





SNAP IN CABLE...
SNAP ON BOX!

ITEM	SIZE	PRICE EACH
DSL38	3/8"	\$0.69




OPEN-BACK SNAP-IN DUPLEX CONNECTOR

- Std. Pkg: 50



SNAP IN



SNAP ON!




ITEM	SIZE	PRICE EACH
DSL38	3/8"	\$1.19

90° OPEN-BACK SNAP-IN CONNECTORS

- Std. Pkg: 50



SNAP IN




SNAP ON!



ITEM	SIZE	PRICE EACH
DSL3890	3/8"	\$0.99
DSL5090	1/2"	\$1.19

SCREW-ON SNAP-IN CONNECTORS

- Std. Pkg: 25



SCREW IN




SNAP ON!




ITEM	FLEX CONDUIT SIZE	DESCRIPTION	PRICE EACH
SNLK-38	3/8"	Screws into the internal threads of 3/8" flexible metal conduits.	\$0.57
SNLK-50	1/2"	Screws into the internal threads of 1/2" flexible metal conduits.	\$0.59

SADDLE-TYPE SNAP-IN CONNECTOR

- Std. Pkg: 25



SET SCREW





SNAP ON!




ITEM	FLEX CONDUIT SIZE	DESCRIPTION	PRICE EACH
SNLK-38SD	3/8"	Clamps saddle on to the external ridges of flexible metal conduits with one screw.	\$0.79

SETScrew SNAP-IN CONNECTOR

- Std. Pkg: 25



SET SCREW



SNAP ON!





ITEM	FLEX CONDUIT SIZE	DESCRIPTION	PRICE EACH
SNLK-38SS	3/8"	One set-screw bites on ridges of flexible metal conduits.	\$0.59

MC CABLE

Snap-In

DUPLEX SNAP-IN CONNECTOR

- Std. Pkg: 25



ITEM	FLEX CONDUIT SIZE	STYLE	DESCRIPTION	PRICE EACH
SNLK-38DU	3/8"	Saddle Clamp	Made for two flexible metal conduits entering a single box or enclosure. One setscrew and saddle combine to securely fasten multiple conductors quickly.	\$0.79


FAST-LOCK CONNECTOR FOR ONE BX/MC CABLE

- Cast metal
- Std. Pkg: 50



ITEM	FITS BOX K.O.	SPECIAL FEATURES	STD. PKG.	PRICE EACH
FLC-50	1/2"	Steel MC Interlocking (MCI) 14-2 (0.470) to 12-4 (0.520) AL MC Interlocking (MCI) 14-2 (0.460) to 12-4 (0.590) Steel AC 14-2 (0.454) to 12-4 (0.556) 1/2" 50 500 AL AC 14-2 (0.485) to 12-4 (0.565) Steel RWFMC, AL RWFMC, AL FMC 3/8"	50	\$0.69
FLC-50L	1/2"	AL MC Interlocking (MCI) 10-3 (0.582) to 8-2 (0.650) Steel RWFMC, AL RWFMC, AL FMC 1/2" Steel AC 10-4 (0.625) to 6-3 (0.842) 1/2" 50 500 AL AC 10-4 (0.625) to 8-4 (0.770) Steel MC Interlocking (MCI) 10-3 (0.594) to 6-2 (0.746)	50	\$0.63
FLC-75L*	3/4"	Steel MC Interlocking (MCI) 10-3 (0.594) to 6-2 (0.746) AL MC Interlocking (MCI) 10-3 (0.582) to 8-2 (0.650) Steel AC 10-4 (0.625) to 6-3 (0.842) 3/4" 25 250 AL AC 10-4 (0.625) to 8-4 (0.770) Steel RWFMC, AL RWFMC, AL FMC 1/2"	50	\$1.29

*Not UL Listed




SNAP ON

**BEST PRICE!
CALL FOR
VOLUME DISCOUNT!**

FITTINGS

FAST-LOCK DUPLEX CONNECTOR

- Cast metal
- Std. Pkg: 50





ITEM	SIZE	SPECIAL FEATURES	PRICE EACH
FLD-50	1/2"	AL MC Interlocking (MCI) 10-3 (0.582) to 8-2 (0.650) Steel RWFMC, AL RWFMC, AL FMC 1/2" Steel AC 10-4 (0.625) to 6-3 (0.842) 3/4" 25 250 AL AC 10-4 (0.625) to 8-4 (0.770) Steel MC Interlocking (MCI) 10-3 (0.594) to 6-2 (0.746)	\$1.99



SNAP ON

90° SNAP-IN SQUEEZE CONNECTORS

- Std. Pkg: 25



ITEM	FLEX CONDUIT SIZE	PRICE EACH
SNLK-3890	3/8"	\$0.89
SNLK-5090	1/2"	\$1.49



STRAIGHT SQUEEZE CONNECTORS



NON-INSULATED

ITEM	SIZE	STD. PKG.	PRICE EACH
SQZ-38	3/8"	50	\$0.45
SQZ-50	1/2"	50	\$0.59
SQZ-75	3/4"	50	\$0.69
SQZ-100	1"	50	\$1.29
SQZ-125	1-1/4"	50	\$1.99
SQZ-150	1-1/2"	50	\$3.99
SQZ-200	2"	5	\$5.99
SQZ-250	2-1/2"	5	\$8.99
SQZ-300	3"	5	\$19.99
SQZ-350	3-1/2"	5	\$49.99
SQZ-400	4"	5	\$69.99

INSULATED

ITEM	SIZE	STD. PKG.	PRICE EACH
SQZ-38I	3/8"	50	\$0.59
SQZ-50I	1/2"	25	\$0.89
SQZ-75I	3/4"	25	\$1.09
SQZ-100I	1"	25	\$1.89
SQZ-125I	1-1/4"	10	\$3.29
SQZ-150I	1-1/2"	10	\$9.99
SQZ-200I	2"	5	\$16.99
SQZ-250I	2-1/2"	5	\$22.99
SQZ-300I	3"	5	\$29.99
SQZ-350I	3-1/2"	5	\$69.99
SQZ-400I	4"	5	\$84.99

MC CABLE

Saddle/Screw-In

90° SQUEEZE CONNECTORS



NON-INSULATED

ITEM	SIZE	STD. PKG.	PRICE EACH
SQZ-3890	3/8"	50	\$0.99
SQZ-5090	1/2"	25	\$1.09
SQZ-7590	3/4"	25	\$1.79
SQZ-10090	1"	25	\$2.99
SQZ-12590	1-1/4"	10	\$4.99
SQZ-15090	1-1/2"	10	\$12.99
SQZ-20090	2"	5	\$17.99
SQZ-25090	2-1/2"	5	\$49.99
SQZ-30090	3"	5	\$69.99
SQZ-35090	3-1/2"	5	\$109.99
SQZ-40090	4"	5	\$179.99



INSULATED

ITEM	SIZE	STD. PKG.	PRICE EACH
SQZ-3890I	3/8"	50	\$1.29
SQZ-5090I	1/2"	25	\$1.39
SQZ-7590I	3/4"	25	\$2.39
SQZ-10090I	1"	25	\$3.99
SQZ-12590I	1-1/4"	10	\$5.69
SQZ-15090I	1-1/2"	10	\$21.99
SQZ-20090I	2"	5	\$27.99
SQZ-25090I	2-1/2"	5	\$67.99
SQZ-30090I	3"	5	\$78.99
SQZ-35090I	3-1/2"	5	\$184.99
SQZ-40090I	4"	5	\$219.99

45° SQUEEZE CONNECTORS




INSULATED

ITEM	SIZE	STD. PKG.	PRICE EACH
SQZ-3845I	3/8"	25	\$2.69
SQZ-5045I	1/2"	25	\$2.69
SQZ-7545I	3/4"	25	\$3.49

MULTI-PURPOSE CABLE CONNECTOR FOR 1/4" K.O.S



• Std. Pkg: 50



ITEM	USE WITH FOLLOWING CABLE	PRICE EACH
MPC25	NM Cable 14/2 to 12/2 Steel/Alum Armored Cable 14/2 to 12/2 Flexible Metal Conduit 3/8"	\$0.89




SQUEEZE-TYPE COMBINATION COUPLINGS (SETSCREW-EMT TO SQUEEZE-FLEX)



ITEM	FLEX SIZE	TO EMT SIZE	STD. PKG.	PRICE EACH
SQZEMT-50	1/2"	1/2"	25	\$1.09
SQZEMT-75	3/4"	3/4"	25	\$2.89
SQZEMT-100	1"	1"	10	\$2.99



STRAIGHT SADDLE CONNECTORS FOR FLEXIBLE METAL CONDUIT




Insulated throat protects wires!



ITEM	SIZE	STD. PKG.	PRICE EACH
DB38IC	3/8"	50	\$0.99
DB50IC	1/2"	50	\$0.99
DB75IC	3/4"	50	\$1.29
DB100IC	1"	25	\$1.79
DB125IC	1-1/4"	25	\$2.49
DB150IC	1-1/2"	25	\$2.99
DB200IC	2"	25	\$3.89
DB250IC	2-1/2"	10	\$8.99
DB300IC	3"	10	\$11.99
DB350IC	3-1/2"	10	\$13.99
DB400IC	4"	10	\$16.99


45° SADDLE CONNECTORS FOR FLEXIBLE METAL CONDUIT



ITEM	SIZE	STD. PKG.	PRICE EACH
DB3845IC	3/8"	50	\$1.19
DB5045IC	1/2"	25	\$1.39
DB7545IC	3/4"	25	\$1.69




90° SADDLE CONNECTORS FOR FLEXIBLE METAL CONDUIT



ITEM	SIZE	STD. PKG.	PRICE EACH
DB3890IC	3/8"	50	\$1.39
DB5090IC	1/2"	50	\$1.39
DB7590IC	3/4"	25	\$1.89
DB10090IC	1"	25	\$3.89



SETScrew CONNECTORS FOR FLEXIBLE METAL CONDUIT



ITEM	FOR FLEX CONDUIT	FITS BOX KNOCKOUT	STD. PKG.	PRICE EACH
BXCN38	3/8"	1/2"	100	\$0.49
BXCN50	1/2"	1/2"	100	\$0.69
BXCN75	3/4"	1/2"	50	\$0.79



MC CABLE

Screw-In / Setscrew

SETSCREW COMBINATION COUPLINGS (THREADED-RIGID TO SETSCREW-FLEX)



ITEM	STYLE	SIZE	STD. PKG.	PRICE EACH
OF694	Setscrew	1/2"	25	\$1.19
OF695	Setscrew	3/4"	25	\$1.49



SCREW-IN CONNECTORS



ITEM	SIZE	STD. PKG.	PRICE EACH
OF671-S	3/8"	50	\$0.59
OF672-S	1/2"	50	\$0.61
OF673-S	3/4"	25	\$1.39
OF674-S	1"	25	\$2.89
OF675-S	1-1/4"	10	\$3.99
OF681-S	1-1/2"	10	\$6.99
OF682-S	2"	10	\$14.29



SCREW-IN COUPLINGS



ITEM	SIZE	STD. PKG.	PRICE EACH
OF676	1/2"	50	\$0.77
OF677	3/4"	25	\$1.39
OF678	1"	10	\$1.99
OF679	1-1/4"	10	\$2.99
OF685	1-1/2"	10	\$3.39
OF686	2"	10	\$6.99



SCREW-IN BUSHINGS





ITEM	SIZE	STD. PKG.	PRICE EACH
FB-50	1/2"	50	\$1.19
FB-75	3/4"	25	\$1.49
FB-100	1"	25	\$1.69



AIR-TIGHT PLENUM FIXTURE WHIP CONNECTORS

• Std. Pkg: 100



Rubber gasket provides air-tight connection.

ITEM	TUBING SIZE	FITS BOX K.O.	PRICE EACH
FMT-38	3/8"	1/2"	\$3.29
FMT-50	1/2"	1/2"	\$4.29



90° AIR-TIGHT PLENUM FIXTURE WHIP CONNECTORS

• Std. Pkg: 100



ITEM	TUBING SIZE	PRICE EACH
FMT-3890	3/8"	\$5.49
FMT-5090	1/2"	\$5.99

ANTI-SHORT INSULATING BUSHINGS



Split body wraps around wires!


ITEM	SIZE	FOR USE WITH	STD. PKG.	PRICE EACH
ASB-0	5/16"	14-2, 14-3, 12-2	20	\$0.04
ASB-1	7/16"	12-4, 10-2, 10-3, 2-1	20	\$0.06
ASB-2	3/8"	14-4, 12-3, 6-1, 4-1	10	\$0.07
ASB-3	1/2"	10-4, 8-2, 8-3, 1-1	10	\$0.08
ASB-4	3/4"	8-4, 6-4, 6-3, 6-2, 4-3, 4-2	10	\$0.09
ASB-5	1"	3-1, 2-1, 2-1/0, 1-300MCM, 1-350MCM, 1-400MCM, 1-450MCM, 1-500MCM	10	\$0.59
ASB-6	1-1/4"	4-1, 4-1/0, 4-2/0, 3-1/0, 3-2/0, 3-3/0, 2-4/0, 1-600MCM, 1-750MCM, 1-800MCM, 1-900MCM	10	\$0.89
ASB-7	1-1/2"	4-3/0, 4-4/0, 3-4/0, 3-250MCM, 3-300MCM, 2-250MCM, 2-300MCM, 2-350MCM, 1-1000MCM	10	\$1.09
ASB-8	2"	4-250MCM, 4-300MCM, 4-350MCM, 4-400MCM, 4-450MCM, 4-500MCM, 3-350MCM, 3-400MCM, 3-450MCM, 3-500MCM, 2-400MCM, 2-450MCM, 2-500MCM	10	\$1.19



NM CABLE

Squeeze/Strain-Relief



TWO-SCREW NM CONNECTORS



ITEM	SIZE	STD. PKG.	PRICE EACH
RXCN38	3/8"	100	\$0.19
RXCN50	1/2"	100	\$0.65
RXCN75	3/4"	50	\$0.69
RXCN100	1"	50	\$1.09
RXCN125	1-1/4"	50	\$1.69
RXCN150	1-1/2"	25	\$2.99
RXCN200	2"	10	\$3.99

MULTI-PURPOSE CABLE CONNECTOR FOR 1/4" K.O.S

• Std. Pkg: 50




ITEM	USE WITH FOLLOWING CABLE	PRICE EACH
MPC25	NM Cable 14/2 to 12/2 Steel/Alum Armored Cable 14/2 to 12/2 Flexible Metal Conduit 3/8"	\$0.89

GARVIN
ELECTRICAL MANUFACTURER

Need A Special Part Made?

WE CUSTOMIZE

Boxes & Covers | Fittings | Hangers & Clamps



Fast Solutions... Designed By You!

CORD GRIP STRAIN-RELIEF CONNECTORS (STEEL)



ITEM	FITS BOX K.O.	CABLE GLAND COLOR	CABLE RANGE		STD. PKG.	PRICE EACH
			MIN	MAX		
CG50250	1/2"	Red	0.15	0.25	100	\$2.99
CG50350	1/2"	White	0.25	0.35	100	\$2.99
CG50450	1/2"	Blue	0.34	0.45	100	\$2.99
CG50560	1/2"	Green	0.45	0.56	100	\$2.99
CG50650	1/2"	Brown	0.55	0.65	100	\$2.99
CG75250	3/4"	Red	0.15	0.25	50	\$3.19
CG75350	3/4"	White	0.25	0.35	50	\$3.19
CG75450	3/4"	Blue	0.35	0.45	50	\$3.19
CG75560	3/4"	Green	0.45	0.56	50	\$3.19
CG75650	3/4"	Brown	0.55	0.65	50	\$3.19
CG75750	3/4"	Yellow	0.65	0.75	50	\$3.19
CG75850	3/4"	Purple	0.75	0.85	50	\$3.19

**CALL FOR
VOLUME
DISCOUNTS!**

847-455-0188

FITTINGS

GROUNDING

Clamps

ZINC GROUND CLAMP FOR BARE WIRE


- Cast metal
- Std. Pkg: 25



ITEM	PIPE SIZE	WIRE RANGE	PRICE EACH
GCBZ50100	1/2" to 1"	8 Solid 2 Stranded	\$1.49



BRONZE GROUND CLAMP FOR BARE WIRE




ITEM	PIPE SIZE	WIRE RANGE	STD. PKG.	PRICE EACH
GCB50100	1/2" to 1"	10 Solid 2 Stranded	25	\$2.89
GCB125200	1-1/4" to 2"	10 Solid 2 Stranded	10	\$4.99
GCB250400	2-1/2" to 4"	10 Solid 2 Stranded	5	\$21.99
GCB450600	4-1/2" to 6"	10 Solid 4 Stranded	5	\$29.99



BRONZE DIRECT-BURIAL GROUND CLAMP

- Direct-burial approved
- Std. Pkg: 25



ITEM	PIPE SIZE	WIRE RANGE	PRICE EACH
GCBB50100	1/2" to 1"	10 Solid 2 Stranded	\$3.99



BRONZE GROUND CLAMP FOR REBAR & BARE WIRE

- Std. Pkg: 25



ITEM	REBAR	WIRE RANGE	PRICE EACH
GCR50100	1/2" to 1"	10 Solid 2 Stranded	\$3.99



DIRECT-BURIAL BRONZE GROUND CLAMP WITH LAY-IN LUG FOR BARE WIRE

- Direct-burial approved
- Std. Pkg: 25




Stainless steel screws

ITEM	PIPE SIZE	WIRE RANGE	PRICE EACH
GCB50100LI	1/2" to 1"	10 Stranded 2 Stranded	\$3.49



BRONZE GROUND CLAMPS FOR ARMORED GROUND WIRE




Clamp secures BX/MC in place

ITEM	PIPE SIZE	WIRE RANGE	STD. PKG.	PRICE EACH
GCA50100	1/2" to 1"	8 Solid 4 Stranded	20	\$2.89
GCA125200	1-1/4" to 2"	8 Solid 4 Stranded	10	\$5.99
GCA250400	2-1/2" to 4"	4, 6, 8 Solid 4 Stranded	5	\$17.99
GCA450600	4-1/2" to 6"	4, 6, 8 Solid 4 Stranded	5	\$27.99



BRONZE GROUND CLAMP, STRAP & HUB ASSEMBLIES

- Chicago approved
- Std. Pkg: 10



ITEM	FOR WATER PIPE	THREADED HUB	WIRE RANGE	PRICE PER ASSY.
GCH5010050	1/2" - 1"	1/2"	10 - 2 Solid	\$5.49
GCH5010075	1/2" - 1"	3/4"	10 - 2 Solid	\$5.99
GCH50100100	1/2" - 1"	1"	10 - 2 Solid	\$7.99





For making connection with no. 4, 6 or 8 AWG copper wire through threaded conduit. Ground wire terminated to set screw.

GROUNDING

Clamps/Tags

THREADED BRONZE GROUND HUBS ONLY



ITEM	THREADED HUB	STD. PKG.	PRICE EACH
H50	1/2"	25	\$3.99
H75	3/4"	25	\$4.99
H100	1"	20	\$5.99



BRONZE GROUND ROD CLAMPS



ITEM	SIZE	STD. PKG.	PRICE EACH
GRC50	1/2"	20	\$1.89
GRC58	5/8"	40	\$1.99
GRC75	3/4"	10	\$2.29



UNIVERSAL GROUND ROD CLAMPS

- Std. Pkg: 25



ITEM	SIZE	PRICE EACH
GRCU	1/2" - 3/4"	\$2.99



NONFERROUS METAL WARNING TAG

- Stamped aluminum
- Std. Pkg: 100





ITEM	PRICE EACH
J-TAG	\$0.69



COPPER SPLIT BOLTS


• Std. Pkg: 10



ITEM	SIZE	MAIN & TAP RANGE OF EQUAL SIZE		MIN TAP WITH 1 MAX MAIN	PRICE EACH
		MIN	MAX		
SBLT-1	1/2"	16 STR	8 STR	16 STR	\$2.09
SBLT-2	3/4"	10 SOL	6 SOL	16 SOL	\$2.29
SBLT-3	1"	8 SOL	4 SOL	16 SOL	\$2.99
SBLT-4	1-1/4"	6 SOL	2 STR	14 STR	\$3.99
SBLT-5	1-1/2"	4 SOL	1/0 STR	14 SOL	\$5.79
SBLT-6	2"	2 SOL	3/0 STR	12 SOL	\$12.99



ALUMINUM LAY-IN LUGS





ITEM	LUG SIZE	DIM A	DIM B	DIM C	STD. PKG.	PRICE EACH
4/14AL	4/14	1-1/16"	3/8"	3/4"	100	\$0.95
1/0-8AL	1/0-8	1-1/12"	5/8"	1-1/8"	100	\$1.69
3/0-6AL	3/0-6	2"	13/16"	1-1/2"	50	\$3.29
250MCM-6AL*	250MCM-6	2-3/16"	13/16"	1-11/16"	50	\$4.59

*Not UL Listed



COPPER LAY-IN LUGS



ITEM	LUG SIZE	DIM A	DIM B	DIM C	STD. PKG.	PRICE EACH
4/14CL	4/14	1-1/16"	3/8"	3/4"	100	\$3.99
1/0-8CL	1/0-8	1-1/12"	5/8"	1-1/8"	100	\$5.99
3/0-6CL	3/0-6	2"	13/16"	1-1/2"	50	\$10.99
250MCM-6CL*	250MCM-6	2-3/16"	13/16"	1-11/16"	50	\$13.99

*Not UL Listed



BREAKER ACCESSORIES


Filler Plates

3/4" NO-SLIP BREAKER FILLER PLATES

- Std. Pkg: 100
- Patented



PEEL



SNAP



STAYS ON... WHEN PANEL COVER IS OFF!

ITEM	FITS THESE BREAKERS	PRICE EACH
BF075SQD	Square D: QO & QOB	\$0.45




1" UNIVERSAL NO-SLIP BREAKER FILLER PLATES

- Std. Pkg: 100
- Patented



PEEL



SNAP



STAYS ON... WHEN PANEL COVER IS OFF!

ITEM	FITS THESE BREAKERS	PRICE EACH
BF100U	General Electric, Cutler-Hammer - "BR" Crouse Hinds, Siemens, Murray, Thomas & Betts, SQUARE D - Homeline, Bryant, Challenger, Westinghouse & many more.	\$0.45




BREAKER ACCESSORIES

Universal Breaker Locks

UNIVERSAL BREAKER LOCKS

- U.S. Patent: 8,598,477
- Std. Pkg: 25



UBL1




UBL1-RED



UBL1-BLU



UBL1-UPC



UBL1-UPC (5-Pack)



ITEM	COLOR	LOCKS ANY ONE-POLE BREAKERS INCLUDING...	PRICE EACH
UBL1	Plated	Bryant, Cutler Hammer, General Electric, ITE Siemens, Square-D, Zinsco, Westinghouse, T&B, Challenger, Eaton & many more!	\$3.29
UBL1-UPC	Plated		\$15.99 (5 Pack)
UBL1-RED	Red		\$3.39
UBL1-BLU	Blue		\$3.39

UNIVERSAL BREAKER LOCK WITH PADLOCK

- U.S. Patent 8,598,477
- Std. Pkg: 1



UBL2 or UBL3



UBL2-UPC

ITEM	COLOR	KEYS	LOCKS THE FOLLOWING BRANDS	PRICE EACH
UBL2	Red	Independent	Bryant, Cutler Hammer, General Electric, ITE Siemens, Square-D, Zinsco, Westinghouse, T&B, Challenger, Eaton & many more!	\$5.99
UBL2-UPC	Red	Independent		\$5.99
UBL3	Red	Single Common (fits all)		\$6.99

BREAKER ACCESSORIES

Universal Breaker Locks

BREAKER LOCK FOR NAVAL SHIPBOARD BREAKERS

- Color: Painted red
- Std. Pkg: 1



ITEM	FITS BREAKERS	SPECIAL FEATURES	PRICE EACH
UBL4	EATON ALB-1	Short leg locks breaker handle in on/off position.	\$6.99

BREAKER LOCK FOR NAVAL SHIPBOARD BREAKERS


- Std. Pkg: 1



ITEM	FITS BREAKERS	SPECIAL FEATURES	PRICE EACH
UBL5	EATON AQB-1	Twisted leg prevents receding as breaker handle is operated.	\$6.99

TWO-POLE UNIVERSAL BREAKER LOCK

- Patented
- Std. Pkg: 10



ITEM	COLOR	LOCKS THESE BRANDS	PRICE EACH
UBL2P	Zinc Plated	Bryant, Cutler Hammer, General Electric, ITE Siemens, Square-D, Zinsco, Westinghouse, T&B, Challenger, Eaton & many more!	\$15.99

BREAKER ACCESSORIES

Universal Breaker Locks/Panel Tags

TWO-POLE UNIVERSAL BREAKER LOCK

- Patented
- Std. Pkg: 10



ITEM	COLOR	LOCKS THESE BRANDS	PRICE EACH
UBL3P	Zinc Plated	Bryant, Cutler Hammer, General Electric, ITE Siemens, Square-D, Zinsco, Westinghouse, T&B, Challenger, Eaton & many more!	\$19.99

ENGRAVED CONTROL PANEL NAMEPLATES

- Made to order
- FAST In-House Engraving
- Std. Pkg: 1
- MADE IN USA



ITEM	SIZE	COLOR	PRICE EACH
TAG-13BUW	1" x 3"	Blue with White Letters	\$2.29
TAG-14BUW	1" x 4"	Blue with White Letters	\$2.49
TAG-13BW	1" x 3"	Black with White Letters	\$2.29
TAG-14BW	1" x 4"	Black with White Letters	\$2.49
TAG-13RW	1" x 3"	Red with White Letters	\$2.29
TAG-14RW	1" x 4"	Red with White Letters	\$2.49

Specify text at time of order.

BEST PRICE *Guaranteed!*
CALL 847-455-0188


P
A
N
E
L
&
P
U
L
L
I
N
G

PULLING ACCESSORIES

Fish/Pull Tapes

SUPER-FLEXIBLE STEEL-COIL FISHTAPE

- Canvas bag included
- Std. Pkg: 1



SUPER FLEX
Easy Pull

ITEM	LENGTH (FT.)	PRICE EACH
FTS-25	25	\$54.99
FTS-35	35	\$65.99
FTS-50	50	\$89.99
FTS-75	75	\$129.99
FTS-100	100	\$164.99

Call for Custom Lengths

NON-METALLIC PLASTIC FISHTAPE



- Std. Pkg: 1



ITEM	LENGTH (FT.)	PRICE EACH
NFT-50	50	\$7.49

POLYESTER CABLE PULLING TAPE

- Sequential foot markings
- Std. Pkg: 1



ITEM	TENSILE STRENGTH (LBS)	LENGTH (FT)	WIDTH	PRICE EACH
PT-1250-3K	1, 250	3, 000	1/2"	\$129.00
PT-1250-5K	1, 250	5, 000	1/2"	\$189.00
PT-1800-3K	1, 800	3, 000	5/8"	\$149.00
PT-1800-5K	1, 800	5, 000	5/8"	\$239.00
PT-2500-3K	2, 500	3, 000	3/4"	\$199.00
PT-2500-5K	2, 500	5, 000	3/4"	\$319.00

LOCATABLE PULLING TAPE WITH TRACER WIRE

- Internally-woven tracer wire
- Std. Pkg: 1



ITEM	TENSILE STRENGTH (LBS)	LENGTH (FT)	PUR UP	PRICE EACH
PTLC-1250-3K	1250	3000	Reel	\$249.00
PTLC-1800-3K	1800	3000	Reel	\$289.00
PTLC-2500-3K	2500	3000	Reel	\$339.00

PULLING ACCESSORIES

Tape, Bender & Sealant

CONDUIT MEASURING TAPE

- Sequential foot markings
- Std. Pka: 1 Spool



ITEM	LENGTH (FT)	TENSILE STRENGTH (LBS)	WIDTH	PRICE EACH
CMT-3000	3, 000 ft.	160 Lbs.	1/4"	\$52.50

SHORT-RADIUS CONDUIT BENDER FOR 1/2" EMT

- Std. Pkg: 1



ITEM	ATTACHMENT	PRICE EACH
SRB-50	Threaded	\$69.00

SHORT-RADIUS CONDUIT BENDER FOR RIGID



ITEM	ALUMINUM EMT	GRC	PRICE EACH
SRB-75	3/4"	1/2"	\$79.00

DUCT SEAL PUTTY

- Std. Pkg: 1



ITEM	SIZE	PRICE EACH
DS1	1 Lb.	\$2.89
DS5	5 Lbs.	\$8.99

NOTE: DS1 & DS5 are not fire-rated.



PRODUCT INDEX

Numerics			
4" Octagon Boxes	176-188	Ceiling Fan Boxes	173, 175, 177-178, 180-182, 184, 186-187
4" Square Boxes	108-126	Ceiling Flange	250
4-11/16" Square Boxes	127-136	Ceiling Tile (T-Bar) Brackets	77-78, 48
5" Square Boxes	137	Ceiling Trim Plates	23-24, 238-239
5" Square Box Assemblies	138-143	CFL Bulbs	1
6" Square Boxes	144-145	CFL Templights	6-7
6" Square Covers/Device Rings	219-220	Chain, Fixture	26
A		Chase Nipples	259
Acorn Clamps	282-283	(Chicago) Plenum Boxes	109, 114, 117-119, 122, 124, 130-132, 135, 176, 180, 183
Adjust. Depth Rings	49-50, 198, 202, 204, 212-213, 217-218, 219-220, 224-226	(Chicago) Plenum Whips	27
Anti-Short Bushings	279	Clamp, Ground	282-285
B		Clamps, Strut	63-64, 94
Bar Hangers	72, 125, 184-186	Clampback Spacer	59
Battleships	76, 158	Clamps, Beam	81-83, 85-87
Beam Clamps	44-48	Colorado Jim Straps	57
Bender, Conduit	291	Compact Fluorescent Bulbs	1
Bodies, Conduit	265-268	Concrete Box Plates	233
Box Open Splice	181, 188	Concrete Form Pipe Inserts	252
Box Spacer Connector	250	Concrete Ring	106-107
Box, Door Jamb Switch	27, 150	Concrete Slab (Box 4" Sq.)	107
Box, Low Voltage Termination	46	Concrete Slab Boxes (Octagon)	106-107
Boxes, 4" Octagon	176-188	Concrete Slab Inserts	252
Boxes, 4" Square	108-126	Conduit Bender	291
Boxes, 4-11/16" Square	127-136	Conduit Bodies	265-268
Boxes, 6" Square	144-145	Conduit Caps	242, 248
Boxes, Ceiling	177-178, 180-182	Conduit Enlarger	258
Boxes, Concrete Slab	106-107	Conduit Hangers	57-70
Boxes, Dual Power/Media	45-46	Conduit Measuring Tape	291
Boxes, Fan	173, 175, 177-178, 180-182, 184, 186-187	Conduit Wing Clip	69
Boxes, Floor	47, 101-102, 104-105	Condulets	265-268
Boxes, Handy	146-149	Connectors, EMT	240-245
Boxes, Masonry	159-167	Connectors, Flex Conduit	272-279
Boxes, Multi-Gang	168-172	Connectors, Liquid Tight	269-271
Boxes, Multi-Gang Switch	156-157	Connectors, Rigid	248-261
Boxes, Pan	173-175	Cord Grips	281
Boxes, Switch	150-155	Couplings, EMT	240-245
Boxes, Tile	159-167	Couplings, Rigid	248-251, 255-259
Boxes, Utility	146-149	Couplings, Slip	241
Brackets, Box Mounting	72-79	Covers, Handy Box	221-223
Brackets, Low Voltage	45-46, 75-76	Cover, Octagon LED Templight	2
Breaker Filler Plates	286	D	
Breaker Locks	287-289	D Rings	39-40
Brick Boxes	159-167	Device Brackets, Low Vol. (Cut-In)	48-49, 75-76
Bridle Rings	35-38	Device Protection Plates	200-201, 203
Bulbs, CFL	1	Device Rings, 4" Octagon	237
Bulb, Horizontal Stabilizer	12	Device Rings, 4" Square	198-205
Bulbs, LED	1	Device Rings, 4-11/16" Square	212-214
Burner Plates, Round (Oil)	235	Device Rings, 5" Square	215-218
Burner Plates, 4" Square (Oil/Gas)	207	Device Rings, 6" Square	219-220
Burner Plates, Handy/Utility (Oil/Gas)	221	Distribution Rings	39-40
Bushed Nipples	259	Door Jamb Switch Box	27, 150
Bushings, Insulating	41-43, 192, 246, 253, 279	Down Light Blank Up	24, 239
Bushings, Reducing	256-257	Drive Rings (Hammer-On)	40
C		Drive Rings (Screw-On)	40
Cable Ties, Self-Cutting	28	Drive Straps	57
Camera Covers	13-19, 51-56, 196-198	Dual Power Boxes	45-46
Can Light Blank Up	24-26, 238-239	Duct Seal	194, 291
Canopy Sets, Pendant	21-22	E	
Caulk, Fire Stop	194	Ear Converters (Old Box Ear Tabs)	189
Ceiling Blank, White	24-26, 238-239	Edge Beam Clamps	68
292	PHONE 847-455-0188	Elbows, EMT	247
		Elbows, Rigid	248-249, 262
		EMT Fittings	240-245
		EMT Couplings, S-Nap-In	240
		Enlarger, Conduit	258
		Extender, 4" Box	115
		Extension Ring, Angled, 4"	123
		F	
		Fan Boxes	173, 175, 177-178, 180-182, 184, 186-187
		Filler Plates, Breaker	286
		Fillers, K.O. Hole	191-192
		Fire Alarm Boxes	128
		Fire Stop	194
		Fishtapes (Steel & Plastic)	290
		Fittings, EMT	240-245
		Fittings, Rigid	248-251, 255-259
		Fittings, Strut	63-64, 92-99
		Fixture Canopy	21-22
		Fixture Hangers, 4" Oct./Round	17-19, 53-55
		Fixture Hangers, 4" Square	13-15, 51-53, 196-198
		Fixture Hangers, 4-11/16" Square	16-17, 55-56, 211
		Fixture Hook	11, 26
		Fixture Pendant Stems	22
		Fixture, Templight Wall Sconce	2
		Flex Connectors	272-279
		Floor Box, Data Ports	47, 105
		Floor Boxes	47, 101-102, 104-105
		Floor Flanges	250
		Foam, Fire Stop	194
		Fork bolts	100
		G	
		G Hooks	33-34
		Galvanized Rigid Conduit Nipples	20, 261
		Gangable Switch Boxes	150-155
		Garvin Covers	206-209
		Goof Ring, Floor Box	103
		Grips, Cord	281
		Ground Clamps	282-285
		Ground, Screws/Clips	188-189
		Ground Tag	284
		Grounding Bushings	264
		Grounding Pigtails	189
		H	
		Handy Boxes	146-149
		Hangers, Bar	72, 125, 184-186
		Hangers, Conduit	57-70
		Hangers, Threaded Rod	89-91
		High Bay Fixture, LED	3
		High Bay Hook	26
		Hole Cover (wall, ceiling)	24-26, 238-239
		Hole Cover, Conduit K.O.	191-192
		Hole Fillers, Breaker	286
		Hole Plug, Rigid, threaded	258
		Hooks, J Cable	29-32
		Hook, J, Multi-Run Trees	32
		Hooks, S	26
		Horizontal Bulb Stabilizer, Templight	12
		Hub, Weatherproof (Meyers)	255
		I	
		Industrial Surface Covers	206-209, 215-216

Prices Subject to Change

garvinindustries.com

PRODUCT INDEX

Insulating Bushings, EMT	41, 246	Pipe Caps	242, 248	Stainless Octagon Boxes 176-177, 179-180	
Insulating Bushings, Rigid	41, 253	Plaster Rings, 4" Square	198-205	Stainless Steel, Reducing Bushings	256
Insulating Bushings, MC/BX	279	Plaster Rings, 4-11/16" Square	212-214	Stainless Steel, Strut Straps	63
J					
J Hooks	29-32	Plaster Rings, 6" Square	219-220	Stainless Steel, Strut Washers	97-98
J Hook, Multi-Run Trees	32	Plenum Fixture-Whip Connector	27, 279	Stand-Off Bracket, Utility	100
J Style Beam Clamp	68	Plenum Fixture Whips	27	Straps, One Hole	58-59
Jack Chain	26	Plugs, Conduit, Flat Floor	246, 252	Straps, Strut	83
Jakes Pull Elbows	242-243, 248-249	Pop Up Floor Box	47, 101-102, 104-105	Straps, Two Hole	60
K					
Knockout Seals	191-192	Pot Light Cover	24-26, 238-239	Strut Fittings	63-64, 92-99
K.O. Insulators	43, 192	Power Leads, Tails	189-190	Strut, Spring Nuts	99
L					
Lamps LED	1	Pull Elbows	248-249, 262	Strut Straps	63
Lamps, CFL	1	Pull Elbows, EMT	247	Stud Plate	44, 71
LED Linear High Bay Fixtures	3	Pulling Tapes	290	Switch Box Extender	158
LED Templights	4-5	Push-In Conduit Hangers	61-62, 65-67	Switch Box Supports	76, 158
LED Wall Pack Fixture	3	Putty, Duct Seal	194, 291	Switch Boxes	150-155
Light Shield, Templight	12	Putty (pad), Fire Stop	194	Swivel Fixture Hangers 4" Rnd / Oct.	17-19, 53-55
Light Socket	10	R			
Liquid Tight Connectors	269-271	Rain Tight Connectors	244	Swivel Fixture Hangers 4" Sq.	13-15, 51-53, 196-198
Lock, Breaker	287-289	Rain Tight Couplings	244	Swivel Fixture Hangers 4-11/16"	16-17, 55-56, 211
Lock, Toggle Switch	27, 158, 205	Recessed Can Light Blank	24-26, 238-239	T	
Locknuts	22, 263	Red 4S Boxes	107, 109, 117-120, 123-125, 126	T-Grid Clips	79
Low Voltage Brackets	45-46, 75-76	Red Heads	279	Tags, Panel	251
Lugs, Grounding	285	Reducer/Enlarger, Rigid Conduit	258	Tapes, Fish (Steel & Plastic)	290
M					
Madison Hangers	76, 158	Reducing Bushings	256-257	Tapes, Pull	290
Magnetic Bridle Rings	35	Reducing Washers	193	Templight, Bulb Stabilizer	12
Masonry Boxes	159-167	Remodel Ring 4" Sq.	48, 76	Templights, CFL	6-7
Masonry/Brick Threaded Rod Stud	88-91	Right Angle Clamps	67	Templights, LED	4-5
Mechanical Lugs (Cu & Al)	285	Rigid Conduit Nipples	20, 261	Templight, LED Octagon-Cover	2
Media Boxes	45-46	Rigid Connectors	248-261	Templight Stringers	6, 7, 10
Metal Stud Grommet	42	Rigid Couplings	248-251, 255-259	Templight, Wall Sconce Fixture	2
Meyers Hub	255	Rigid Fittings	248-251, 255-259	Templights, Fixture Only	8-10
Multi-Gang Boxes	168-172	Rings, Bridle	35-38	Threadless Rigid Connector	248
Multi-Gang Covers	229-232	Rings, Distribution	39-40	Threaded Bushed Nipples	259
N					
Nail Straps	57	Rings, Drive	40	Threaded Deck Hanger, Mtg. Plate	90
Nipples, Chase	259	Rod, Threaded Studs	89-91	Threaded Plug	258
Nipples, Galvanized Rigid	20, 261	Romex Connector	280	Threaded Rigid Couplings	251
Nipples, Offset	242, 245, 258	S			
No-Thread Connector	249	S Hooks	26	Threaded Rod Hangers	88-91
Nose Plates	45-46	Safety Plate	44, 71	Threaded Rod Studs	90
Nuts, Spring, Strut	99	Sconce, Wall, Templight Fixture	2	Three Piece Couplings	251
O					
Octagon Boxes, 4"	176-188	Seal Tight Connectors	269-271	Three Piece Knockout Seals	191
Octagon-Cover Templight, LED	2	Seal, Duct	194, 291	Ties, Cable, Self-Cutting	28
Offset Connector, EMT	242, 245	Seals, K.O.	191-192	Toggle Switch Lock	27, 158, 205
Offset Device Rings	199	Service Drop Plate	100	Two Hole Straps	60
Offset Nipples	242, 245, 258	Service Entrance Caps	260	Two Piece Connector	245
Oil Burner Plates	207, 221, 235	Shatter Guard, Templight	11	U	
Old Work Ears & Clips	158	Slick Rods	89	U Washer, Strut	97
One Hole Straps	58-59	Slip Couplings	241	Utility Boxes	146-149
Open Splice Box	181, 188	Snap In Flex Connectors	272-279	V	
P					
Pads, Fire Stop	194	Socket, Light	10	Vandal Proof Conduit Caps	242
Pan Boxes	1783-175	Split Bolts	285	W	
Panel Tags/Nameplates	289	Split Grounding Bushings	264	Wall Pack Fixture, LED	3
Parallel Beam Clamps	68	Split Insulating Bushings	41-42, 246, 253	Wall Sconce, Templight Fixture	2
Pendant Stems	22	Spools, Backboard	40	Washers, Bar Joist	91
Pennies, Steel	253	Spring Nuts	99	Washers, Octagon	98
Pigtails	189-190	Spring Steel Conduit Hangers	61-62, 65-67	Washers, Reducing	193
Q					
R					
S					
T					
U					
V					
W					

PRODUCT PART NUMBER INDEX

Numericals							
1/0-8AL	285	52C11	199	72C1	210	52151-AB	111
1/0-8CL	285	52C12	199	72C1-RED	210	52151-ABBX	111
3/0-6AL	285	52C12-1	199	72C1-VT	210	52151-ABR	111
3/0-6CL	285	52C12-3/4	199	72C1-VTRED	210	52151-B	112
3PC50 - 3PC600	251	52C13 - 52C62A	199	72C3-F - 72C3-2	214	52151-BBX	112
4/14AL	285	52C13SQ - 52C23SQ	199	72C4-5/8	214	52151-BLNK	108
4/14CL	285	52C13-SS - 52C62A-SS	198	72C4S-1/2	212	52151-BLNKSS	108
4SSLD-1/2	148	52C14-5/8	199	72C4S-3/4	212	52151-BR	112
5BC	217	52C17 - 52C25	202	72C6	210	52151-BX	110
5CP	217	52C17SQ - 52C25SQ	202	72C6-VTSS	210	52151-DWS	112
5PF5075	138	52C17-SS - 52C24-SS	202	72C13 - 72C62A	212	52151-F	111
5PF5075AB	138	52C20A	202	72C17 - 72C20A	213	52151-FBX	111
5SQ5075	137	52C20A-SS	202	72C29 - 72C42	215	52151-FR	112
5SQ5075OW	137	52C20-SS	202	72C44 - 72C51	216	52151-FS	111
5SQ50100	137	52C21-SS	202	72CP	210	52151-MS	112
5SQ100125	137	52C22SQ & 52C23SQ	199	72EXR-F - 72EXR-2	214	52151-MSBX	112
5SQ5075100	137	52C24	202	73C1-VT	210	52151-MSR	112
5SQBLNK	137	52C24-SS	202	250MCM-6AL	285	52151-OW	110
6BC	219	52C25	202	250MCM-6CL	285	52151-OWBX	110
6CP	219	52C26 & 52C28	199	5150 - 51200	217	52151-OWR	110
12WFS	98	52C50 - 52C125	15, 52, 198	5250 - 52200	218	52151-R	110
12WFSS	98	52C50-WH - 52C125-WH	15, 53, 198	6150-BLNK	144	52151-RED	109
13WFS	98	53C1-VT	195	6150-EXT	145	52151-S	109
13WFSS	98	54C1	234	6150-S	144	52151-SDR	109
14WFS	98	54C1-R	234	6250-1	144	52151-SPT	109
14WFSS	98	54C1-RED	234	6250-1-1/4	144	52151-SVT	109
17AB	39	54C1-VT	234	6250-3/4	144	52151-SVTRED	109
17BB	39	54C3-F - 54C3-2	237	6250-BLNK	144	52151-SVTSS	110
17CB	39	54C3-RED	237	6250-EXT	145	52151-SWB	113
23WBJ	91	54C6	234	6250-S	144	52151-WB	113
24WBJ	91	54C6-R	234	6350-1	145	52151-WBBX	113
51AMR-1	217	54C6-VTSS	234	6350-1-1/2	145	52151-WBR	113
51AMR-158	217	54C40	235	6350-1-1/4	145	52171-1	118
52AMR-1	218	54C41	235	6350-3/4	145	52171-1/2	116
52AMR-158	218	54C42	235	6350-BLNK	144	52171-1/2DR	116
52AMR-2	218	54C50 - 54C125	19, 55, 236	6350-EXT	145	52171-1DR	118
52C1	195	54C50-WH - 54C125-WH	19, 46111	6350-S	145	52171-1RED	119
52C1-OCT	50, 235	54CBPO	235	46111	173	52171-1RED	119
52C1-RED	195	55C1-VT	234	46111-OW	173	52171-1VT	119
52C1-TOG	195	61-1/2 - 61-2	219	46111-R	173	52171-3/4	117
52C1-VT	195	61AMR-1	219	46112	173	52171-3/4-1	118
52C1-VTRED	195	61AMR-158	219	47111	174	52171-3/4-1VT	118
52C3-1/2U - 52C3-3/4U	15, 205	62-1/2 - 62-2	220	52141-1/2	108	52171-3/4AB	120
52C3-F - 52C3-2	205	62AMR-1	220	52151-1/2	108	52171-3/4ADR	117
52C4-5/8	16, 204	62AMR-158	220	52151-1/2DR	108	52171-3/4F	120
52C6	195	63-ADJ	220	52151-3/4	108	52171-3/4RED	117
52C6-VT-SS	195	63AMR-3	220	52151-3/4AB	111	52171-3/4VT	117
52C09 - 52C12-1	199	72C0-5/8	214	52151-3/4DR	108	52171-3/4-VT	117
52C10	199			52151-3/4F	111	52171-AB	120
				52151-3/4RED	109	52171-ABBX	120
				52151-3/4VT	109	52171-ABR	120
						52171-ABX	120
						52171-ABR	120
						52171-BLNK	116
						52171-BLNKSS	116

PRODUCT PART NUMBER INDEX

52171-BX	119	52191-OWRED	126	54151-VT	176	56112	175
52171-F	120	52191-RED	126	54171-1/2	179	56113	174
52171-FBX	121	52191-S	126	54171-3/4	179	57111	175
52171-FR	121	53141-1/2	108	54171-BLNK	179	72151-3/4	127
52171-FRED	120	53151-1/2	114	54171-BLNKSS	179	72151-S	127
52171-FS	120	53151-3/4	114	54171-BX	180	72151-SVT	127
52171-KOR	116	53151-3/4RED	114	54171-DE	179	72171-1	131
52171-MS	121	53151-BLNK	114	54171-DEOW	179	72171-1-1/4	131
52171-MSBX	121	53151-RED	114	54171-F	187	72171--1-1/4VT	132
52171-MSR	121	53151-S	114	54171-FAN	187	72171-1-1/4W	131
52171-OW	119	53151-SUB	115	54171-FANBH	186	72171-1/2	129
52171-OWBX	119	53151-SVT	114	54171-FANNB	180	72171-1/2W	129
52171-OWR	119	53151-SVTSS	114	54171-FANNBWP	180	72171-1RED	131
52171-OWRED	119	53171-1	123	54171-FANOW	186	72171--1-VT	131
52171-R	119	53171-3/4	123	54171-FANWP	187	72171-1W	131
52171-RED	117	53171-A45	123	54171-FBX	187	72171-3/4	129
52171-S	117	53171-BLNK	122	54171-FOPR	188	72171-3/4-1	130
52171-SBB	118	53171-RED	122	54171-FR	187	72171-3/4-1VT	131
52171-SDR	117	53171-S	122	54171-JBR	187	72171-3/4-1W	131
52171-SPT	117	53171-SUB	122	54171-JBX	187	72171-3/4RED	129
52171-SVT	118	53171-SVT	122	54171-OPR	181	72171-3/4-VT	130
52171-SVTRED	118	53171-SVTSS	122	54171-OW	179	72171-3/4W	129
52171-SVTSS	118	54151-1/2	176	54171-OWBX	181	72171-BLNK	129
52171-SWB	121	54151-3/4	176	54171-OWR	181	72171-BLNKSS	129
52171-WB	121	54151-BLNK	176	54171-R	181	72171-BLNKW	129
52171-WBBX	121	54151-BLNKSS	176	54171-RED	180	72171-BXW	132
52171-WBR	122	54151-BX	177	54171-S	180	72171-FBXW	132
52181-1	125	54151-DE	176	54171-SBB	180	72171-FSW	132
52181-1/2-SPKR	107, 124	54151-DEOW	177	54171-SVT	180	72171-MSBXW	132
52181-1-SPKR	124	54151-F	178	54171-SVTSS	180	72171-MSW	132
52181-3/4	123	54151-FAN	178	54171-TBAR	181	72171-RED	130
52181-3/4-SPKR	107, 124	54151-FANBH	184	54171-TBFN	181	72171-S	130
52181-3/4-SPKRR	107, 124	54151-FANNB	177	54181-BLNK	181	72171-SVT	130
52181-AB	125	54151-FANNBWP	177	54181-OW	182	72171-SVTRED	130
52181-BLNK	123	54151-FANOW	184	54181-S	181	72171-SVTSS	130
52181-FRED	125	54151-FANWP	178	54181-TBAR	182	72171-SW	130
52181-FS	125	54151-FBX	178	55151-1/2	182	72181-1	133
52181-L	124	54151-FR	178	55151-3/4	182	72181-1-1/2	133
52181-OW	125	54151-HU	185	55151-BLNKSS	182	72181-1-1/4	133
52181-OWRED	125	54151-HUBX	185	55151-RED	183	72181-3/4	133
52181-RED	124	54151-HUR	185	55151-S	182	72181-BLNK	133
52181-S	124	54151-J	178	55151-SVTSS	183	72181-DTA	133
52181-SPKR	107, 123	54151-JBX	178	55151-VT	182	72181-DTAB	133
52181-SPKRR	123	54151-JR	178	55171-BLNKSS	183	72181-S	133
52181-SVT	124	54151-OW	176	55171-RED	183	73151-S	127, 134
52181-VTBAR	78, 125	54151-OWBX	177	55171-S	183	73151-SW	134
52191-1	126	54151-OWR	179	55171-SVT	183	73171-1	135
52191-3/4	126	54151-R	177	55181-S	183	73171-1-1/4W	135
52191-BLNK	126	54151-RED	177	56111	174	73171-1/2	134
52191-FRED	126	54151-S	176	56111-OW	174	73171-1W	135
52191-OW	126	54151-SVTSS	177	56111-R	175	73171-3/4	134

PRODUCT PART NUMBER INDEX

73171-3/4W	134	BC18KC2	66	BP-1936	207	CBD-1200	24, 238
73171-BLNK	134	BC18KC38	66	BP-19350	221	CBP	233
73171-BLNKW	134	BC18KC112	66	BPO-1935	207	CBP-3/8	233
73171-RED	135	BC18KC114	66	BPO-1936	207	CBP-AP	233
73171-S	134	BC18KC1234	66	BPO-19350	221	CBP-APO	233
73171-SUB	135	BC18KC1234SM	67	BR-100-WS - BR-200-WS	36	CBP-B	233
73171-SVT	135	BC18ST	84	BR-125 - BR-400	36	CBP-VT	233
73171-SVTSS	135	BC516	84	BR-125-SS - BR-400-SS	35	CBS-800 - CBS-1200	26, 239
73171-SW	135	BC516KC1	66	BR-150NP - BR-400NP	38	CCN-50 - CCN-400	243
73181-BLNK	136	BC516KC2	66	BR-150NPWH	38	CCN-50I - CCN-400I	243
73181-SW	136	BC516KC38	66	BR-150-SSC - BR-400-SSC	37	CCNR-50 - CCNR-400	244
82171-RD	128	BC516KC112	66	BR-150-SSCWH	38	CCP-50 - CCP-400	244
82171-WH	128	BC516KC114	66	BR-150-TW - BR-400-TW	37	CCPR-50 - CCPR-400	244
		BC516KC1234	66	BR-150-WH - BR-400-WH	36	CG50250 - CG75850	281
		BC516ST	84	BR-150-WHWS	37	CH-50 - CH-500	61
ABS	188	BC916	84	BR-200NPWH	38	CHB-50 - CHB-50100	69
ABS6	188	BC916ST	84	BR-200-SSCWH	38	CHB-75 - CHB-100	69
AMR-00	237	BC-1024	83	BR-200-WHWS	37	CHBC-50 - CHBC-200	65
AMR0	204	BC-1420	83	BR-501024 - BR-2001024	36	CHN-50I - CHN-600I	259
AMR1	198	BC-1420-SS	82	BRM75BK - BRM125BK	35	CHN50-SS - CHN400-SS	259
AMR-1-LV	49	BC-1420-XWM	83	BRM75WH - BRM125WH	35	CHN-50100 - 100100	259
AMR2	202	BC-3816	83	BRM150-HD - BRM400-HD	35	CHO-5025-SM - 10075-	67
AMR-2-LV	50	BC-3816-SS	82	BRS150 & BRS200	38	CHO-5025-TM - 10075-	65
AMR3	224	BCRC	70	BW98	46	CHOKR-1	100
AMR4	225	BCSM-5075 - BCSM-125	67	BXCN38 - BXCN75	277	CHOKR-2	100
AMR5	225	BCTM-5075 - BCTM-125	66			CHP-50 - CHP-100	61
AMR6	226	BCX - BCX916	84			CHP-50-SM - CHP-100-	66
AMR011B	213	BEX-450 & BEX-475	115	C105651MED	1	CHP-50-TM - CHP-100-	65
AMR111B	212	BF075SQD	286	C105652MOG	1	CHPA-50 - CHPA-100	62
AMR158	198	BF100U	286	CAPE50 - CAPE400	242	CHPR-50 - CHPR-100	69
AMR211B	212	BH3	78	CAPR50 - CAPR600	248	CHPT-50 - CHPT-100	70
APS	91	BHA1	72	CAT150-AB - CAT400-AB	34	CHQ-50 & CHQ-75	61
APSKC1	70	BHA1C	72	CAT-150ABMAG - 400AB.	33	CHQT-50 & CHQT-75	61
APSKC1234	70	BHA16	72	CAT150 - CAT400	34	CHSS-50 - CHSS-400	60
ASB-0 - ASB-8	279	BHA24	72	CAT150-MAG - CAT400	33	CJ	57
		BHAD16	72	CAT150-WMAG - CAT400	33	CJIN	57
		BHAD24	72	CAT150-WM - CAT400-WM	33	CLB-50 - CLB-600	59
BA-1/4	91	BHC	80	CB-1250	167	CLBU	59
BAKC38	62	BHT1	77	CB-1350	167	CLC-800	23, 239
BAKC1234	62	BHT1A	77	CB-2250	167	CLS	10
BAT-3/8	91	BHT1HD	77	CB-2350	167	CMT-3000	291
BB-1/2-2	250	BHT481A	77	CB-3250	167	CPMH1	26
BB-1/2-1	250	BHTC	80	CB-3350	167	CPMH1-VT	26
BB-1/2 & BB-3/4	250	BMB1U	73	CBC-275	25, 238	CS812	57
BB4-6	73	BMB3U	73	CBC-350	25, 238	CS812D	57
BB4-25	73	BMB4S3P	74	CBC-600 - CBC-1200	24, 239	CS912D	57
BB4-26	73	BMB4S4P	74	CBC-275800	25, 238	CSLP-50 - CSLP-400	244
BB6-26	73	BMB16SL	72	CBC-350800	25, 238	CT46-308SC	28
BC1	82	BMB616SL	72	CBC-F	25, 238	CT46-308UVBSC	28
BC18	84	BOP-164	90	CBCU	25, 238	CT46-311SC	28
BC18KC1	66	BP-1935	207	CBD-800 - CBD-1200	24, 238	CT46-311UVBSC	28
BC18KC1SM	67						

A

B

C

PRODUCT PART NUMBER INDEX

CT46-314SC	28	EMT-5090 - EMT-40090	247	G600-BX	151	G1939-SS	206
CT46-314UVBSC	28	EMT-7545 - EMT-40045	247	G600-OW	151	G1940	208
CTB-24	48, 78	EMTNM-38	243	G600-OWBX	151	G1941	209
CTB-244S	48, 78	EXR-F - EXR-2	15, 204	G600-OWR	151	G1942	209
CTMBK	28	EZ143102	272	G600-R	151	G1943	209
CTMVBK	28			G601	152	G1944	209
CWC-38 - CWC-125	69			G601-3/4	152	G1947	207
		F		G601BVR	151	G1947-SS	207
		FB	100	G601BVROW	151	G1948	209
		FB-50 - FB-100	42, 278	G601-BX	152	G1949	209
D		FB330C	101	G601-F	152	G1950	208
DB38IC - DB400IC	277	FB400C	101	G601-FBX	152	G1950-SS	208
DB3845IC	277	FBCF-BR	103	G601-FR	152	G1951	209
DB3890IC	277	FBCF-SS	103	G601-OW	152	G1952	209
DB5045IC	277	FBCVBR-1TR-KIT	102	G601-OWBX	152	G19180	146
DB5090IC	277	FBCVBR-3D-KIT	47, 105	G601-OWR	153	G19180-BLNK	146
DB7545IC	277	FBCVBR-GTR-KIT	104	G601-R	153	G19190	221
DB7590IC	277	FBCVBR-TRWR-KIT	105	G602	153	G19279	146
DB10090IC	277	FBCVBR-U-KIT	47, 104	G602-3/4	153	G19280	146
DCB	79	FBCVGRBK	103	G602-BX	153	G19280-E	149
DEX-150 & DEX-175	200	FBCVR-BR-FC	101	G602-F	153	G19281	146
DEX-250 & DEX-275	203	FBCVR-SS-FC	101	G602-FBX	154	G19281-3/4	147
DEX-275	203	FBCVSS-1TR--KIT	102	G602-FR	154	G19281-AB	148
DEX-350 - DEX-950	228	FBCVSS-3D-KIT	47, 105	G602-OW	153	G19281-BLNK	146
DEX-375 - DEX-975	228	FBCVSS-GTR-KIT	104	G602-OWBX	154	G19281-BLNKSS	146
DJSK	27, 150	FBCVSS-U-KIT	47, 104	G602-OWR	154	G19281-E	149
DJSKWH	27, 150	FBF-BR	102	G602-R	154	G19281-ESS	149
DLC	76	FBF-SS	102	G603	154	G19281-F	148
DPB-2	46	FBL	100	G603-3/4	154	G19281NGH	147
DPB-2F	46	FF50 - FF600	250	G603-BX	155	G19281-SS	146
DPB-2OW	46	FFCP-50 - FFCP-100	246, 252	G603-F	154	G19282	147
DPBNP	45	FFE50 - FFE75	250	G603-FBX	155	G19282-3/4	147
DPBOSDUP	45	FLC-50	274	G603-FR	155	G19282-AB	148
DPBOSGFI	45	FLC-50L	274	G603-OW	155	G19282-BLNK	147
DRS-1/2 - DRS-1-1/2	40	FLC-75L	274	G603-OWBX	155	G19282-BLNKSS	147
DRV-1/2 - DRV-1-1/2	40	FLD-50	275	G603-OWR	155	G19282-ESS	149
DS1 & DS5	194, 291	FMT-38 & FMT-50	27, 279	G603-R	155	G19282-F	149
DSL3890	273	FMT-3890 & -5090	27, 279	G1929	206	G19282NGH	147
DSL5090	273	FSCLK10	194	G1929-SS	206	G19282-SS	147
DSL38	272	FSFOM	194	G1930	208	G19290	221
DSL38	272	FSPAD	194	G1932	208	G19290-SS	221
DSL38	272	FTS-25 - FTS-100	290	G1933	208	G19320	221
DST-200 - 1200	39			G1934	208	G19350	221
DST-200-P - 500-P	39			G1935	206	G19380	221
		E		G1935-SS	206	G19390	222
E5075 - E125150	258	G100	42	G1936	207	G19420	222
EC	189	G500	150	G1936-SS	207	G19430	222
ECS-50 - ECS-75	242	G500-BX	150	G1937	208	G19470	222
EDG50 - EDG300	68	G500-OW	150	G1938	206	G19530	222
EF50 - EF100	252	G500-OWBX	150	G1938-SS	206	G20281	149
EFL50 - EFL100	252	G500-OWR	150	G1939	206	G20290	223
EMS5090 - EMS10090	245	G600	151				
EMT-5045 - EMT-40045	247						

PRODUCT PART NUMBER INDEX

G20320	223	HP-100 - HP-1200	139	KOBR-50	43, 192	MC50 - MC400	268
G20350	223	HP-200 - HP-2200	141	KOBS-50 & KOBS-75	43, 192	MCC-1213	86
G20380	223	HP1929 - HP1949	142	KOS-50 - KOS-600	191	MCC-1213BK	86
G20430	223	HP1933 - HP1952	143	KOS-50-OT-KOS-400-OT	191	MCC-3410	86
G20470	223	HPAB-100 - HPAB-1200	140	KOS-50-OTSS-400-OTSS	191	MCC-3410BK	86
GB-1582 - GB-1589	168	HPAB-200 - HPAB-2200	141	KOS-50-VT - KOS-600-VT	191	MCC-3816	86
GB-2122 - GB-2125	170	HPAB-AMR1	140	KP18AMR	74	MCC-3816BK	86
GB-2126 - GB-2129	171	HPAB-AMR2	142			MCC-5811	86
GB-2122341-GB-2125341	170	HPAB-AMR158	140			MCC-5811BK	86
GB-2126341-GB-2129341	171	HPAB-AMR258	142	LB50 - LB400	265	MFC-1213	85
GBBC-2 - GBBC-9	232	HP-AMR1	139, 141	LC50 - LC400	267	MFC-3410	85
GBD-350	156	HP-AMR158	139	LED40 - LED150	1	MFC-3816	85
GBDC-122 - GBDC-124	224	HP-AMR258	141	LFCU	21	MFC-5811	85
GBDC-125 - GBDC-126	225			LFS-16WHT	22	MGSB-2	156
GBDC-127 - GBDC-129	226			LFS-375-12WH - 60WH	22	MGSB-2F	156
GBDC-342 - GBDC-344	224	IB-50 - IB-400	41, 246	LFS-375-NUT	22	MGSB-2OW	156
GBDC-345 - GBDC-346	225	IBS-50 - IBS-400	41, 246	LHB-804 - LHB-3255	3	MGSB-3	156
GBDC-347 - GBDC-349	226	IBT-50 - IBT-600	41, 253	LL50 - LL400	266	MGSB-3F	156
GBDUP-2 - GBDUP-9	229	IBTS-50 - IBTS-600	42, 253	LN-38 - LN600	263	MGSB-3OW	156
GBEX-1582 - GBEX-1589	169			LNG-50 - LNG-600	263	MGSB-4	157
GBEX-2122 - GBEX-2129	172	JC-100	26	LNS-50 - LNS-600	263	MGSB-4F	157
GBGFI-2 - GBGFI-9	231	JCL50 - JCL350	68	LNSS-50 - LNSS-200	263	MGSB-4OW	157
GBP-158-F - GBP-15834	227	JFC-1213	85	LR50 - LR400	266	MLB50 - MLB400	266
GBP-212-F - GBP-21234	227	JFC-1420	85	LT50 - LT400	267	MLL50 - MLL400	266
GBSD-3150 - GBSD-4375	227	JFC-3816	85	LTC-38 - LTC-600	269	MLR50 - MLR400	267
GBTC-2 - GBTC-9	230	JFC-5811	85	LTC-3845 - LTC-40045	271	MOGADP	12
GC	189	JFCS-3816	83	LTC-3890 - 40090	270	MOGENLG	12
GCA50100 - GCA450600	283	JFCS-3816SS	83	LTCSS-38 - 200	269	MOLB-100 - MOLB-400	265
GCB50100 - GCB450600	282	JHK-12-AB - JHK-64-AB	30	LTCSS-5090 - 20090	270	MOLT-100 - MOLT-400	265
GCB50100LI	283	JHK-12ABMAG - 64ABMAG	30	LVP1	45	MPC25	276, 280
GCBB50100	282	JHK-12-ABSS - 64-ABSS	29	LVP1DH	45	MSCH-1	57
GCBZ50100	282	JHK-12-BC1	31	LVP1NP	45	MSCH-1234	57
GCH5010050	283	JHK-12-BW2 - 64-BW2	32	LVP1SH	45	MT50 - MT400	267
GCH5010075	283	JHK-12-HO516 - JHK-64-	31	LVP2	45	MX1CG - MX6CG	268
GCH50100100	283	JHK-12-HO916 - JHK-64-	31	LVP2NP	46		
GCHK50 - GCHK600	264	JHK-12-HO - JHK-64-HO	31	LVP3NP	46		
GCR50100	282	JHK-12 - JHK-84	29	LVP41 - LVP42D	203	N	
GLTC-38 - GLTC-600	269	JHK-12MAG - JHK-84MAG	30	LVP51 - LVP52	213	NFT-50	290
GLTC-3845 - 40045	271	JHK-12SS - JHK-64SS	29	LWP-305 - LWP-1355	3	NMLT-38 - NMLT-200	269
GLTC-3890 - 40090	270	JHK-21-BC - JHK-64-BC	31			NMLT-3890 - 20090	270
GRC50 - GRC75	284	JHK-21-BW6 & JHK-32-	32			NS-50 - NS-100	57
GRCU	284	JHT-212 - JHT-646	32				
GS	188	J-TAG	284	M			
GSC-5075	13, 51, 196			MBC-1024	81	O	
GSCR-5075	17, 53, 236			MBC-1213	81	OCA-35050 - OCA-40075	106
GSST	188	KC1T	62	MBC-1213WM	81	OCC-50 - OCC-75	245
		KC38T	62	MBC-1213XL	82	OCN50 - OCN400	258
		KC114T	62	MBC-1420	81	OCR-200 - OCR-600	107
H50 - H100	284	KC1234T	62	MBC-1420-SS	81	OCR-400FAN	107
HC50 - HC100	251	KCB-50100 - KCB-100125	69	MBC-1420WM	81	OCR-300341 - -400341	107
HP-0000	138	KOB-50 - KOB-150	43, 192	MBC-3816	81	OCS-50 - OCS-100	242
				MBC-3816EV	82	ODR-250 - ODR-375	40
				MBC-3816-SS	81	OF671-S - OF682-S	278
				MBC-3816WM	81	OF676 - OF686	278

PRODUCT PART NUMBER INDEX

SNSS1213	99	TB-125	159	TBX-625	162	TRH-3816	89
SNSS1420	99	TB-125-G	159	TBX-635	166		
SNSS3816	99	TB-125-OW	153	TC-5075	70		
SNWO1213	99	TB-135	163	TCAB	79	UBL1	287
SNWO1420	99	TB-135-G	163	TCSM	79	UBL1-BLU	287
SNWO3816	99	TB-135-OW	155	THS-25 - THS-400	60	UBL1-RED	287
SOB-1	100	TB-225	159	THSR-50 - THSR-600	60	UBL1-UPC	287
SOCN-50	240	TB-225-G	159	THSS-38 - THSS-400	59	UBL2	287
SP-3-MS & SP-6-MS	44, 71	TB-235	163	THSSR-50 - THSSR-400	60	UBL2P	288
SP-3 & SP-6	44, 71	TB-235-G	163	TL40LEDPT - TL150	6	UBL2-UPC	287
SP-9 - SP-24	44, 71	TB-325	159	TL40LED - TL150LED	5	UBL3	287
SP-33 - SP-58	44, 71	TB-325-F	156, 159	TL40LEDWS - TL150	5	UBL3P	289
SP-312 - SP-524	44, 71	TB-325-G	159	TL40LEDW - TL150LEDW	5	UBL4	288
SQZ-38I - SQZ-400I	275	TB-335	163	TL60WP - TL100WP	5	UBL5	288
SQZ-38 - SQZ-400	275	TB-335-F	157, 163	TL105CF	6	UGB-50 - UGB-600	264
SQZ-3845i- SQZ-7545I	276	TB-335-G	163	TL105CF277	6		
SQZ-3890I - SQZ-40090I	276	TB-425	159	TL105CF277W	6	WBF-1	48, 75
SQZ-3890 - SQZ-40090	276	TB-425-F	157, 160	TL105CF277WS	7	WBF-2	49, 75
SQZ-5045- SQZ-40045	276	TB-425-G	160	TL105CFPT	7	WBF-4	48, 76
SQZEMT-50 - -100	243, 276	TB-435	163	TL105CFW	6	WDS	40
SRB-50	291	TB-435-F	157, 164	TL105CFWS	7	WDSM S	40
SRB-75	291	TB-435-G	164	TLCO	2	WDSWS	40
SSCN-50I - SSCN-400I	241	TB-525	160	TLF	8	WH50-SS - WH400-SS	255
SSCN-50 - -400	240, 241	TB-525-F	157	TLF-FC	12	WH50 - WH400	255
SSCP-50 - SSCP-400	241	TB-525-G	160	TLF-FCL	12	WHG50 - WHG400	255
SSLP-50 - SSLP-400	241	TB-535	164	TLF-L	9	WPP1	200
STE50 - STE200	63	TB-535-G	164	TLFLMAGW	9	WPP2G	203
STF14	88	TB-625	160	TLF-LW	9	WPPDUP	201
STF14NP	89	TB-625-G	160	TLF-LWS	9	WPPTOG	201
STF0024	89	TB-635	164	TLFMAGW	8	WPPU	201
STF0030	89	TB-635-G	164	TLFW	8		
STF0036	89	TB-725-G	160	TLFWS	8		
STF1424	88	TB-735-G	164	TLH	11		
STF1430	88	TB-825-G	161	TLHS	12		
STF1436	88	TB-835-G	165	TLM	10		
STF1448	88	TB-925-G	161	TLMAGW	10		
STR50-SS - STR600-SS	63	TB-935-G	165	TLMC	11		
STR50 - STR600	63	TB-1025-G	161	TLMPT	10		
STU50 - STU200	63	TB-1035-G	165	TLMU	2		
SW-1/4-G - SW-5/8-G	97	TBD-250	167	TLMW	10		
SW-1/4-SS - SW-3/4-SS	97	TBD-350	167	TLPS	12		
SW-1/4 - SW-3/4	97	TBX-125	162	TLPS-L	12		
SW-2-3/8 - SW-2-3/4	98	TBX-135	166	TLSG	11		
		TBX-225	162	TLSGLK	11		
		TBX-235	166	TLSGW	11		
TAG-13BUW	289	TBX-325	162	TLU-60 - TLU-100	4		
TAG-13BW	289	TBX-335	166	TOGLOK	27, 158, 205		
TAG-13RW	289	TBX-425	162	TOGLOKRD	27, 158, 205		
TAG-14BUW	289	TBX-435	166	TOGLOKWH	27, 158, 205		
TAG-14BW	289	TBX-525	162	TPC-50 - TPC-100	245		
TAG-14RW	289	TBX-535	166	TRH-1420	89		

U

W

T

CUSTOM easier & faster than you think


You pick a product... We customize In-House!

PAINTING




Boxes - Covers - Fittings
J-Hooks - Hangers/Supports

CUTTING




Conduit - Threaded Rod
Hangers - Supports - Strut

ELBOWS / NIPPLES



Any Length - Any Size
EMT or Rigid

BOXES / COVERS



We Can Modify Any Box to Meet
Your Job Requirements


NEW INVENTIONS

GOT A
PRODUCT
IDEA?



We Can Build It!

STAINLESS



Custom Boxes - Hubs - Bridle
Rings - J-Hooks - Beam Clamps

GARVIN
ELECTRICAL MANUFACTURER

847-455-0188
garvinindustries.com

NEW LABOR SAVING PRODUCTS... FASTER INSTALLS

PROVEN TO SAVE YOU MONEY!



**HINGED PREFAB
 BOX ASSEMBLIES**

Page 139, 143



**WEATHERPROOF
 LED CORN LAMPS**

Page 1



**SNAP-IN EMT
 FITTINGS**

Page 240



**CONCRETE SLAB
 BOX ASSEMBLIES**

Page 106



**EMT SLIP
 COUPLINGS**

Page 241, 244




**48" T-BAR
 BRACKET**

Page 77



**PREFAB BRACKET
 BOX CONNECTOR**

Page 250



**2 & 3 POLE UNIVERSAL
 BREAKER LOCKS**

Page 288-289

Theft Resistant LED Templights

Starting at:
\$120.00



Fast Customization

- Professional Painting
- Custom Cutting
- Prefab Assemblies
- KO Punching
- Box Modifications

