



Catalog  
C18



ICC tailors its solutions to small and medium-sized installers to help them win more projects.

## Small & Mid-sized Installers



## High Profit Margin

ICC prices are low, up to 60% lower compared to the big brands; so our Elite Installers can increase their margin and win more projects.

ICC focuses only on non-spec projects. We help our Elite Installers win those projects over the expensive spec brands.

## Non-Spec Projects






## Value Distribution Network

ICC distributors share the same value as ICC, we work together to keep our prices low.

ICC offers end-to-end structured cabling solutions with nine product categories as a single vendor solution, so our Elite Installers have no compatibility issues from mixing vendors.

## One Vendor



## Ease of Installation

ICC engineers its products to keep installation simple, minimizing training time and reducing labor cost.

# Join the Elite



## Elite Installer™



- Free membership
- 15-Year Performance Limited Warranty
- Project discounts
- Sales promotions
- Free product samples and demos
- New product releases
- Reward points

## Certified Elite Installer™



- Paid membership
- All benefits from Elite, plus:
- Lifetime Performance Limited Warranty
- One free Master Technician Training Course included
- Free unlimited site verifications
- Free tools


## Master Technician Training

- One-day course
- Earn a Master Technician License
- BICSI® certified
- Earn BICSI Continuing Education Credits
- Hands-on training

Visit [icc.com/elite](http://icc.com/elite) to sign up and learn more about the Elite Installer program.


# Table of Contents

- 01 Work Area Outlets
- 25 Patch Panels and Cross-connect
- 35 Premise Cables
- 39 Fiber Optic System
- 49 Racks and Cable Management
- 69 Residential Enclosures
- 77 Cords and Cable Assemblies
- 81 Raceway and Wiring Ducts
- 85 Tools and Accessories
- 90 Part Number Index



This catalog is an overview of our wide product selection. Visit us online at [icc.com](http://icc.com) for our full line of products, detailed information, tech specs, and installation instructions.

© 2018, ICC. ICC and the ICC logo are a registered trade name and trademark. All rights reserved. The materials contained here are protected by copyright, trademark, and other intellectual property laws and may not be copied, modified, or used in any unauthorized manner without the express, written permission from ICC. All other trade names and trademarks are the property of their respective owners.



# Work Area Outlets




## High Density (HD) Keystone Jacks





Colored wiring diagram



Rear split-back IDC



50µ" gold plated contacts



Terminate and trim wires in one squeeze



Free JackEasy™ included

### HD Keystone Jacks

- Exceeds TIA-568 performance

CAT 6A FTP	IC1078S6A0
CAT 6A UTP	IC1078GAxx <sup>2</sup>
CAT 6	IC1078F6xx <sup>1</sup>
CAT 5e	IC1078F5xx <sup>1</sup>
6P6C	IC1076F0xx <sup>1</sup>

### 25-Pack ValuePacks

- Packaged in a resealable bag
- Reduces packaging waste
- Lowers the cost per unit

CAT 6	IC107F6Cxx <sup>2</sup>
CAT 5e	IC107F5Cxx <sup>2</sup>
6P6C	IC1076FCxx <sup>3</sup>

<sup>2</sup>Available in: WH, IV, BL, OR, RD, BK

<sup>3</sup>Available in: WH, IV

### 400-Pack ValuePacks

- Packaged in a resealable box
- Ten jacks per bag, forty bags per box
- Lowers the cost per unit

CAT 6	IC107F6Vxx <sup>4</sup>
CAT 5e	IC107F5Vxx <sup>4</sup>
6P6C	IC1076FVWH


<sup>4</sup>Available in: WH, BL

<sup>1</sup>Color Options:  
See more at icc.com





Six HD jacks in a Décorex™ insert



## HD in the Work Area

With a narrow body, up to six HD keystone jacks can be installed in a Decorex™ insert to maximize usage of space. Installing CAT 6A keystone jacks require standard spacing between ports to reduce alien crosstalk.



Up to 48 ports in 1 RMS



Narrow body reduces space



TIA® Component Rated




CAT 6A: 360° zinc-alloy shielding



## HD in the Telecom Closet

HD keystone jacks can help maximize connectivity in the telecom closet by providing up to 48 ports of connectivity within one rack mount space.



Easy (EZ®)  
Keystone Jacks



Colored wiring diagram



In-line 110 IDC



Cap terminated wires



Terminate and trim wires in one squeeze



Free JackEasy™ included

### EZ Keystone Jacks

- Unshielded Twisted Pair (UTP)
- Exceeds TIA-568 performance

CAT 6	IC1078L6xx <sup>1</sup>
CAT 5e	IC1078E5xx <sup>1</sup>
6P6C	IC1076V0xx <sup>1</sup>

### 25-Pack ValuePacks

- Packaged in a resealable bag
- Reduces packaging waste
- Lowers the cost per unit

CAT 6	IC107L6Cxx <sup>2</sup>
CAT 5e	IC107E5Cxx <sup>2</sup>
6P6C	IC1076VCxx <sup>3</sup>

<sup>2</sup>Available in: WH, IV, BL, OR, RD, BK

<sup>3</sup>Available in: WH, IV

### 400-Pack ValuePacks

- Packaged in a resealable box
- Ten jacks per bag, forty bags per box
- Lowers the cost per unit

CAT 6	IC107L6Vxx <sup>4</sup>
CAT 5e	IC107E5Vxx <sup>4</sup>
6P6C	IC1076VVWH

<sup>4</sup>Available in: WH, BL

<sup>1</sup>Color Options:  
See more at [icc.com](http://icc.com)






Easy to grip



Six EZs in a single gang



Comes pre-kitted in surface mount boxes




Mobile Patch Boxes



## EZ<sup>®</sup> in the Work Area


EZ keystone jacks work with a wide variety of faceplates, surface mount boxes, mounting boxes, and mobile patch boxes.



24 ports in 1 RMS



Easy to service and manage




TIA® Component Rated



## EZ® in the Telecom Closet

With a wider body, EZ keystone jacks are staggered on patch panels to allow for easy insertion and removal.



Install in faceplates



Install in blank patch panels

## Couplers & Inserts



Available in resealable bags

### Keystone Couplers

- HD style
- TIA® Component Rated
- No termination required
- 50 micro-inch gold plated contacts
- For patch cable extension

#### 25-Pack ValuePacks

CAT 6	IC107C6CBK
CAT 5e	IC107C5CBK

#### Single

CAT 6A	IC107C6Axx*
CAT 6	IC107CP6xx*
CAT 5e	IC107C5Exx*
6P6C Pin 1-6	IC107C6Sxx*
6P6C Pin 1-1	IC107C6Rxx*

\*Color Options:  
See more at [icc.com](http://icc.com)







LC 10G Duplex



LC Duplex



SC Simplex



ST Simplex

### Fiber Optic Couplers

- HD style
- Female/Female
- Feed-through – front and rear
- Ceramic or metal sleeves
- Supports multimode or single-mode

LC 10G Duplex	IC107LCGxx*
LC Duplex	IC107LC2xx*
SC Simplex	IC107SC2xx*
ST Simplex	IC107ST2xx*



### Voice Phone Couplers

- Connects line cords together
- 50 micro-inch gold plated contacts

8P8C, Pin 1-1, F to F	ICMA3508DR
6P6C, Pin 1-6, F to F	ICMA350A6C
6P6C, Pin 1-1, M to 2F	ICMA267D66



### Blank Fill-In & Feed-Through Insert ValuePacks

- HD style
- Fills open and unused ports
- Pass cable through a 0.30" diameter hole

<b>Fill-in</b>	
100-Pack ValuePack	IC107BNVxx*
10-Pack ValuePack	IC107BN0xx*
<b>Feed-Through</b>	
10-Pack ValuePack	IC107BN2WH

\*Color Options:    
See more at [icc.com](http://icc.com)  
WH IV



# Audio & Video Connectors



Install in residential enclosures



Matches decorator style outlets



100% digital A/V signals



Angled to reduce space



### HDMI Couplers

- HD style
- Supports 1080p, 3D, and HDCP
- 99.99% oxygen free conductors
- 24k gold plated connectors

Female/Female IC107HDMxx\*  
 90° Female/Female IC107AHMWH

### HDMI Décorex™ Inserts

- Works with Décorex faceplates
- Includes two blank modular inserts

1 HDMI, 2 HD Ports IC107DH2xx\*  
 2 HDMI, 2 HD Ports IC107DDHxx\*

\*Color Options:  
 See more at [icc.com](http://icc.com)





### Dual Audio Speaker Connectors

- HD style
- Patented design
- Red and black push buttons
- Molded (+) and (-) signs

Rear crimp-on  
Rear buttons

IC107DSCxx\*  
IC107DSBxx\*

### Binding Post Audio Speaker Connectors

- Gold plated posts
- Posts work with banana plugs
- Marked red and black for polarity

Pair of HD connectors IC107PMGWH



### RCA Jacks

- HD style
- Gold plated
- High quality audio and video
- 6-Pack includes: two red, one green, one blue, one white, and one blank module

**RCA/RCA**  
Red insert  
6-Pack

IC107R6GWH  
IC107RR5WH

**RCA/F-Type**  
White insert

IC107BFGWH

**RCA/IDC**  
Red insert  
White insert

IC107R8GWH  
IC107B8GWH

### 3.5mm Stereo Audio Speaker Couplers

- HD style
- Works with 3.5mm plugs

Female/Female  
Female/Push-pin

IC107SACWH  
IC107SAPxx\*



### F-Type Video Jacks


- HD style
- Female/Female
- Threaded to secure connection
- Works with RG-6 and RG-59 coaxial cable
- F-Type Compression Tool and Connectors, see page 88

Nickel plated, 3 GHz	IC107B9Fxx*
Gold plated, 3 GHz	IC107B9Gxx*
Nickel plated, 2 GHz	IC107B5Fxx*
Gold plated, 2 GHz	IC107B5Gxx*
RG-6Q, compression	IC107FQGWH

### 25-Pack ValuePacks

- Packaged in a resealable bag
- Reduces packaging waste
- Lowers the cost per unit

Nickel plated, 3 GHz	IC107BFDWH
Gold plated, 3 GHz	IC107BGDWH
Nickel plated, 2 GHz	IC107BFCWH
Gold plated, 2 GHz	IC107BGCWH



### BNC Video Jacks


- HD style
- Nickel plated
- Supports CCTV, NTSC analog video signals, and satellite link signals

75 Ohm	IC107BNCxx*
50 Ohm	IC107B3Gxx*

### USB Couplers

- HD style
- Female/Female

90°, A-to-A, USB 3.0	IC107AUSWH
A-to-A, USB 3.0	IC107UAAWH
A-to-B, USB 2.0	IC107UABWH


\*Color Options:    
See more at [icc.com](http://icc.com)  
WH IV



Home theater solutions



VGA: analog video



### Décorex™ Audio and Video Inserts



- Works with Décorex faceplates
  - Durable ABS plastic
- |                    |             |
|--------------------|-------------|
| 1 HDMI, 2 HD Ports | IC107DH2xx* |
| 2 HDMI, 2 HD Ports | IC107DDHxx* |
| 1 VGA, 2 HD Ports  | IC107DR2xx* |
| 1 VGA, 4 HD Ports  | IC107DR4xx* |
| 8 Binding Posts    | ICRDSQBpxx* |
| 3 RCA, 1 F-Type    | ICRDS3RFWH  |
| 1 F-Type           | IC630DSFxx* |

\*Color Options:  
See more at icc.com





# Faceplates & Inserts



### Décorex™ Faceplates

- Decorator style outlets
- Configurable with inserts
- Smooth glossy finish
- Durable ABS plastic

- 1 Insert, Single Gang IC107DFSxx\*
- 2 Inserts, Double Gang IC107DFDxx\*
- 3 Inserts, Triple Gang IC107DFTWH
- 4 Inserts, Quad Gang IC107DFQWH



#### Stainless Steel

- 1 Insert, Single Gang IC107DFSSS
- 2 Inserts, Double Gang IC107DFDSS

### Décorex™ Inserts

- Configurable with connectors

- Blank IC630DIBxx\*
- 1 Port IC107DI1xx\*
- 2 Ports IC107DI2xx\*
- 3 Ports IC107DI3xx\*
- 4 HD Ports IC107DI4xx\*
- 6 HD Ports IC107DI6xx\*

\*Color Options:    
See more at [icc.com](http://icc.com)  
WH IV




Accepts A/V connectors



Accepts HD and EZ® connectors



Double gang, 12 ports



Six EZs in a single gang



### Classic Faceplates

- Durable ABS plastic
- Rugged texture finish
- Fits NEMA size outlet box

#### Single Gang

Blank	IC630EB0xx*
1 Port	IC107F01xx*
2 Ports	IC107F02xx*
3 Ports	IC107F03xx*
4 Ports	IC107F04xx*
6 Ports	IC107F06xx*

#### Double Gang

Blank	IC630EBDxx*
8 Ports	IC107FD8xx*
12 Ports	IC107F12xx*



Tab lock box

### 25-Pack ValuePacks

- Packaged in a resealable box
- Reduces packaging waste
- Lowers the cost per unit

1 Port	IC107F1Cxx*
2 Ports	IC107F2Cxx*
3 Ports	IC107F3Cxx*
4 Ports	IC107F4Cxx*

\*Color Options:  
See more at icc.com







Oversized: 22% larger



### Integrated Faceplates with IDC Termination

- One-piece design
- Durable ABS plastic
- Rugged texture finish

CAT 5e & F-Type ICRDS0F5WH  
 6P6C & CAT 5e ICRDSV05WH  
 6P6C, CAT 5e, & F-Type ICRDSVF5WH



### Oversized Integrated Faceplates with IDC Termination


- Designed to cover uneven and oversized drywall cuts
- Larger than standard faceplates
- Durable ABS plastic
- Rugged texture finish

CAT 5e & F-Type ICRDS0FLWH  
 6P6C & CAT 5e ICRDSV0LWH  
 6P6C, CAT 5e, & F-Type ICRDSVFLWH



### Configurable Stainless Steel

Blank	IC630EBSSS
1 Port	IC107SF1SS
2 Ports	IC107SF2SS
3 Ports	IC107SF3SS
4 Ports	IC107SF4SS
6 Ports	IC107SF6SS



### Configurable Station ID

1 Port	IC107S01xx*
2 Ports	IC107S02xx*
3 Ports	IC107S03xx*
4 Ports	IC107S04xx*
6 Ports	IC107S06xx*



### Configurable Telephone

1 Port, ABS plastic	IC107FFWxx*
1 Port, stainless steel	IC107FFWSS



### Configurable Stainless Steel with ID

1 Port	IC107S01SS
2 Ports	IC107S02SS
3 Ports	IC107S03SS
4 Ports	IC107S04SS
6 Ports	IC107S06SS




### HD Configurable Furniture

<b>NEMA</b> Opening: 1.83" H x 2.60" W x 0.19" D	
4 HD Ports	IC107FN4xx*
<b>TIA</b> Opening: 1.33" H x 2.60" W x 0.19" D	
4 HD Ports	IC107FT4xx*



### Configurable Furniture

<b>Modular</b> Opening: 1.30" H x 2.56" W x 0.19" D	
3 Ports	IC107FM3xx*



**Integrated**

F-Type  
2 F-Type

**With Screw Termination**

6P6C  
2 6P6C  
6P6C and F-Type

IC630EG0xx\*  
IC630EGGxx\*

IC630E60xx\*  
IC630E66xx\*  
IC630E6GWH



**Configurable Oversized**

• 3.12" W x 4.87" H

1 Port  
2 Ports  
3 Ports  
6 Ports

IC107LF1xx\*  
IC107LF2xx\*  
IC107LF3xx\*  
IC107LF6xx\*



**Configurable Angled**


1 Port  
2 Ports  
4 Ports

**With Station ID**

4 Ports, 2 flat/2 angled

IC107DA1xx\*  
IC107DA2xx\*  
IC107DA4xx\*

IC107AS4WH



**Telephone**

**Phillips Screw Termination**

6P6C

**IDC Termination**

6P6C, stainless steel

IC630DB6xx\*

IC630DA6SS



**Configurable Electrical**

**Faceplate**

2 Ports, Single Gang

**Insert**

2 Ports  
4 HD Ports

IC106FP2xx\*

IC107DPIxx\*  
IC1074PIxx\*



**Bulk Nose**

**Single Gang**

Opening: 1.25" W x 0.90" D

**Double Gang**


Opening: 2.75" W x 1.15" D

IC640BSSxx\*

IC640BDSxx\*

\*Color Options:  
See more at [icc.com](http://icc.com)





12 port box works with raceway



### Classic Configurable

- Two-piece design; cover and base
- Durable ABS plastic
- Includes adhesive strips and wood screws for mounting

1 Port  
2 Ports  
4 Ports  
6 Ports  
12 Ports

IC107SB1xx\*  
IC107SB2xx\*  
IC107SB4WH  
IC107SB6WH  
IC107SBTxx\*

## Surface Mount & Mounting Boxes





### 25-Pack ValuePacks

- Packaged in a tab lock box
- Reduces packaging waste
- Lowers the cost per unit

1 Port  
2 Ports

IC107BC1xx\*  
IC107BC2xx\*



Elite boxes are raceway compatible



### Classic Kitted

- Kitted with EZ keystone jacks
- CAT 5e or voice
- Includes adhesive strips and wood screws for mounting

#### CAT 5e

1 Port, 1 Connector IC625S51xx\*  
 2 Ports, 2 Connectors IC625S52xx\*

#### 6P6C

1 Port, 1 Connector IC625SV1V  
 2 Ports, 2 Connectors IC625SV2V

### Elite™ Configurable

- Two-piece design; cover and base
- Works with raceway and magnets
- Includes icons and mounting hardware: adhesive strips and wood screws

1 Port  
 2 Ports  
 4 Ports  
 6 Ports


IC108SB1xx\*  
 IC108SB2xx\*  
 IC108SB4xx\*  
 IC108SB6xx\*

\*Color Options:  
 See more at [icc.com](http://icc.com)





Cables need to be pulled through the box prior to mounting



Base and raceway can be mounted prior to pulling cable

### Mounting Boxes

- Durable ABS plastic
- Includes cable ties, adhesive strips, and wood screws for mounting

Single Gang  
Double Gang

IC107MRSxx\*  
IC107MRDxx\*

### Junction Boxes

- Two-piece design; box and base
- Durable ABS plastic
- Includes cable ties, adhesive strips, and wood screws for mounting

Single Gang  
Double Gang

ICACSMBSxx\*  
ICACSMBDxx\*



Double washers



### Surface Mount Jacks

- Supports voice applications
- Phillips screw down terminals
- Includes adhesive strips and wood screws for mounting

8P8C  
8P4C  
8P8C with RJ-31x

IC625SB8IV  
IC635DS4xx\*  
IC635DS8xx\*

### Mobile Patch Boxes

- Six ports of connectivity
- Works with magnets to mount on flat metal surfaces

Configurable  
CAT 6  
CAT 5e  
Magnet, 2 pcs.

IC107MB6BK  
ICMPPMB606  
ICMPPMB506  
ICMAGBLOCK



# Patch Panels & Cross-connect



## Rack Mount Patch Panels





750 plug-jack mating cycles




100+ re-termination



CAT 6A vertical IDC reduces crosstalk



Solderless PCB



50 micro-inch gold



### Patch Panels

- TIA® Component Rated
- IEEE 802.3 PoE Plus
- Fits 19" EIA rack mount widths
- Data Color Icons and Dust Caps, see page 31

#### 24 Port, 1 RMS

CAT 6A ICMPP0246B  
 CAT 6 ICMPP02460  
 CAT 5e ICMPP0245E  
 6P6C, USOC ICMPP024U6

#### 48 Port, 2 RMS

CAT 6A ICMPP0486B  
 CAT 6 ICMPP04860  
 CAT 5e ICMPP0485E  
 6P6C, USOC ICMPP048U6

### 6-Pack ValuePacks

- Packaged in a resealable box
- Reduces packaging waste
- Lowers the cost per unit

#### 24 Port, 1 RMS

CAT 6 ICMPP2460V  
 CAT 5e ICMPP245EV

#### 48 Port, 2 RMS

CAT 6 ICMPP4860V  
 CAT 5e ICMPP485EV



HD single row



HD/EZ® staggered row



HD dual row



### Configurable Blank Patch Panels

- Configurable with modular connectors
- Fits 19" EIA rack mount widths

#### 24 Port

HD Single, 1 RMS IC107BP241  
 HD/EZ Staggered, 1 RMS IC107BE241

#### 48 Port

HD Dual, 1 RMS IC107BP481  
 HD Dual, 2 RMS IC107BP482



### Configurable CAT 6A UTP Patch Panels

- 24 ports
  - TIA® Component Rated
  - Shielded wire caps
  - Protects against alien crosstalk
  - Staggered ports reduce crosstalk
- |               |       |            |
|---------------|-------|------------|
| <b>Kitted</b> | 1 RMS | ICMPP246AU |
| <b>Blank</b>  | 1 RMS | IC107PPU6A |

### Configurable CAT 6A FTP Patch Panels

- 24 ports
  - Shielded 360°
  - Steel frame construction
  - Protects against EMI/RFI
  - Pre-installed grounding studs
- |               |       |            |
|---------------|-------|------------|
| <b>Kitted</b> | 1 RMS | ICMPP246AS |
| <b>Blank</b>  | 1 RMS | IC107PPS6A |

**Grounding Accessories**  
 Wire, 10-Pack ICACSGK6AS  
 Kit ICACSGKS00



Up to 48 ports in 1 RMS

### Feed-Through Patch Panels

- TIA® Component Rated
  - Pre-installed keystone couplers
  - No termination required
  - 50 micro-inch gold plated contacts
- |                |               |            |
|----------------|---------------|------------|
| <b>24 Port</b> | CAT 6, 1 RMS  | ICMPP24CP6 |
|                | CAT 5e, 1 RMS | ICMPP24CP5 |

- |                |               |            |
|----------------|---------------|------------|
| <b>48 Port</b> | CAT 6, 1 RMS  | ICMPP48C61 |
|                | CAT 6, 2 RMS  | ICMPP48CP6 |
|                | CAT 5e, 1 RMS | ICMPP48C51 |
|                | CAT 5e, 2 RMS | ICMPP48CP5 |



### Voice Patch Panels with Telco Connectors

#### 8P2C

- Active pins: 4 and 5

#### Male

24 Port, 1 RMS  
48 Port, 2 RMS

ICMPP24T2C  
ICMPP48T2C

#### Female

24 Port, 1 RMS  
48 Port, 2 RMS

ICMPP24TF2  
ICMPP48TF2

#### 8P4C

- Active pins: 4/5 and 3/6

#### Male

24 Port, 1 RMS  
48 Port, 2 RMS

ICMPP24T4C  
ICMPP48T4C

#### Female

24 Port, 1 RMS  
48 Port, 2 RMS

ICMPP24TF4  
ICMPP48TF4

#### 6P2C

- Active pins: 3 and 4

#### Male

24 Port, 1 RMS  
48 Port, 2 RMS

ICMPP024T2  
ICMPP048T2

#### Female

24 Port, 1 RMS

ICMPP024F2

#### 6P4C

- Active pins: 3/4 and 2/5

#### Male

24 Port, 1 RMS  
48 Port, 2 RMS

ICMPP024T4  
ICMPP048T4


#### Female

24 Port, 1 RMS

ICMPP024F4



The panel can be reversed



## Wall Mount Patch Panels



### Integrated with IDC Termination

- 12 ports
- TIA® Component Rated
- Install on wall and racks
- 10" H x 3.30" W x 2.40" D
- Two-piece design; patch panel with 89D mounting bracket

CAT 6 ICMPP12V60  
 CAT 5e ICMPP12V5E  
 6P6C, USOC ICMPP012U6

**Patch Panel Color Icons**  
 Data Icons, 120-Pack ICMPPICSxx\*

**Dust Cover ValuePacks**  
 10-Pack ICACSDCICL  
 100-Pack ICACSDCVCL

### 6-Pack ValuePacks

- Packaged in a resealable box
- Reduces packaging waste
- Lowers the cost per unit

CAT 6 ICMPP1260V  
 CAT 5e ICMPP125EV

\*Color Options:       
 WH BL RD YL GN





### Front Access Zero-U Patch Panels

- 12 ports
  - TIA® Component Rated
  - Install on wall
  - 110-Type IDC terminations
  - Removable cover
- |        |            |  |
|--------|------------|--|
| CAT 6  | ICMPP12F6E |  |
| CAT 5e | ICMPP12F5E |  |




### Configurable Blank Patch Panels

- Install on wall
  - 10" H x 3.30" W x 2.40" D
  - Configurable with modular connectors
  - Two-piece design; patch panel with 89D mounting bracket
- |               |            |  |
|---------------|------------|--|
| 12 HD Ports   | IC107BP12V |  |
| 8 HD/EZ Ports | IC107BP8VB |  |




With Feet


# 110 Wiring



Hinged



Without Feet



Rack Mount

## Kits

- Includes a wiring block with feet
- Includes 110 connecting blocks

### CAT 5e

100-Pair	IC110W1004
300-Pair	IC110W3004
100-Pair, Hinged	IC110H1004

### CAT 6

96-Pair	IC110WK966
---------	------------

## Wiring Blocks

100-Pair with Feet	IC110WF100
300-Pair with Feet	IC110WF300
100-Pair without Feet	IC110NF100
100-Pair, Hinged	IC110WH100

### Cable Managers

With Feet	IC110CMBWF
Without Feet	IC110CMBNF

## Patch Panels

96-Pair CAT 6 Kit
100-Pair
200-Pair
Cable Manager

IC110PRK61
IC110RM100
IC110RM200
IC110RMCMB

## Accessories

### Connecting Blocks 100-Packs

4-Pair	IC110CB4PC
5-Pair	IC110CB5PC


### Other

Label Holder, 6-Pack	IC110LHLDR
Wire Cap, 50-Pack	IC110TC450



Clear Cover

# 66 Wiring



## 50-Pair Wiring Blocks

25-Pack ValuePack IC066NBC50  
Single Block IC066NB050

## Pre-wired Blocks

- Includes 89D Mounting Bracket
- Includes Removable Hinged Cover

**Data**  
12 Ports, 8P8C IC06628P8C

**Voice**  
8 Ports, 6P6C IC06686P6C  
12 Ports, 6P4C IC06626P4C

**Telco**  
1 25-Pair Female IC066SFT25  
2 25-Pair Female IC066DFT50

## 89B Mounting Brackets

25-Pack ValuePack ICMB89BCWH  
Single Bracket ICMB89B0WH

## Accessories

Block Clear Cover IC066CV050  
Bridge Clips, 100-Pack IC066BRCLP

**Spools 10-Pack ValuePacks**  
Built-in wood screw ICACSWDS20  
Without screw ICACSWDS10






# Premise Cables



REELEX II® tangle-free coiling



Pull box packaging



REELEX II® box design





CAT 6A reel packaging



Big payout tube


## Packaging

Premise cables come packaged in a double-layered carton which strengthens the carton's durability to prevent tearing. CAT 6A premise cables come packaged on a wooden reel to reduce stress when pulling cable.



## Performance

ICC Premise Cables are tested to meet and exceed TIA® industry performance standards and comply with the strict TIA, UL®, and RoHS® (Restriction of Hazardous Substance) standards.



CAT 6A: available in UTP and FTP




Sequential footage markings




Bare solid copper



X separator: reduces crosstalk



Rip cord: easy jacket removal



**CAT 6A 650 MHz**

- 1000 feet per reel

**UTP**

Riser ICCABR6Axx<sup>1</sup>  
Plenum ICCABP6Axx<sup>1</sup>

<sup>1</sup>Available in: BL, WH

**FTP**


Riser ICCABR6FBL  
Plenum ICCABP6FBL



**CAT 6e UTP 600 MHz**

- 1000 feet per box

Riser ICCABR6Exx<sup>2</sup>  
Plenum ICCABP6Exx<sup>2</sup>



**CAT 6 UTP 500 MHz**

- 1000 feet per box

Riser, no tape separator ICCABR6Vxx<sup>2</sup>  
Plenum, tape separator ICCABP6Vxx<sup>2</sup>




**CAT 5e UTP 350 MHz**

- 1000 feet per box

Riser ICCABR5Exx<sup>2</sup>  
Plenum ICCABP5Exx<sup>2</sup>

<sup>2</sup>Color Options:






# Fiber Optic System




## Enclosure Solutions

LGX® compatible fiber optic enclosures include covers and doors to protect fiber connectivity. Wall mount enclosures come with a locking door to provide extra protection for installations in unsecured areas.



## Panel Solutions

Fiber optic patch panels provide a cost-effective solution in an open frame environment. LGX® compatible panels are configurable with fiber adapter panels and MPO cassettes making moves, adds, and changes easy.



# Fiber Optic Enclosures





Removable covers



### Rack Mount Enclosures, 12.6" Depth

- Configurable with LGX® compatible adapter panels and LGX compatible MPO cassettes
- 20 GA steel, powder-coated black
- Slide-out tray
- Holds one splice tray
- Fits 19" EIA rack mount widths

3 Panel, 1 RMS	ICFORE31RM
6 Panel, 2 RMS	ICFORE62RM
12 Panel, 4 RMS	ICFORET4RM
12 fiber splice tray	ICFOSKFM12

### Rubber Grommets, 20-Pack

25.4mm (1 RMS)	ICFORECAC2
38.10mm (2 & 4 RMS)	ICFORECAC3




### Wall Mount Enclosure, 3.5" Depth

- Configurable with LGX compatible adapter panels and LGX compatible MPO cassettes
- Single locking door design
- Includes four hook and loop Velcro® cable ties
- Holds one splice tray
- 10.75" H x 13" W

4 Panel	ICFODE41WM
12 fiber splice tray	ICFOSKFM12

### Rubber Grommets, 20-Pack

38.10mm	ICFORECAC3
---------	------------



### HD LC Quad Fiber Patch Panel, 96 Fibers

- Loaded with 24 LC to LC quad adapters
- Fits 19" EIA rack mount widths
- Includes dust caps

LC quad patch panel, 10G aqua adapters, 1 RMS

ICFP96ML1G

## Fiber Optic Connectivity



### Blank Fiber Patch Panel

- Configurable with LGX compatible adapter panels and LGX MPO cassettes
- Fits 19" EIA rack mount widths

3 Panel, 1 RMS

ICFORPP1RM



LGX compatible footprint



288 fibers in 4 RMS



LC-LC 24 fibers



LC-LC 12 fibers



SC-SC 12 fibers



ST-ST 6 fibers

### Adapter Panels

#### LC to LC

- 24 fibers, MM, 10G, aqua
- 24 fibers, MM, beige
- 24 fibers, SM, blue
- 12 fibers, MM, 10G, aqua
- 12 fibers, MM, beige
- 12 fibers, SM, blue

#### Blank Panel

Blank, cover unused panel openings

- ICFOPL161G
- ICFOPL1615
- ICFOPL1619
- ICFOPL16BG
- ICFOPL16B5
- ICFOPL16BK

ICFOPB00BK

#### SC to SC

- 12 fibers, MM, 10G, aqua
- 12 fibers, MM, beige
- 12 fibers, SM, blue
- 6 fibers, MM, beige
- 6 fibers, SM, blue


#### ST to ST

- 6 fibers, MM, beige
- 6 fibers, SM, blue

- ICFOPC161G
- ICFOPC16BK
- ICFOPC26BK
- ICFOPS16BK
- ICFOPS26BK

- ICFOPT16BK
- ICFOPT26BK

MM = Multimode, SM = Single-mode



Removable snap-in cassette

## HD Cassette Patch Panels



Rear male MPO connectors

### HD MPO Cassette Panels

- Built with pre-terminated LC or SC to MPO cassettes
- One MPO connector supports twelve fibers
- Interchangeable cassettes, remove using a screwdriver
- Fits 19" EIA rack mount widths
- Includes dust caps
- Supports migration from 10G to 40G and 100G

	LC 24 Fibers	SC 12 Fibers
OM3, 50/125	ICFC24MLPG	ICFC12MSPG
OM2, 50/125	ICFC24MLP5	ICFC12MSP5
OM1, 62.5/125	ICFC24MLP6	ICFC12MSP6
OS1, 9/125	ICFC24SLP9	ICFC12SSP9



# MPO Cassettes




### MPO Cassettes

- LGX compatible footprint
- Factory terminated and tested
- Includes dust caps and performance results
- Low Insertion Loss of <0.5dB
- Equipped with male MPO connectors on the rear


	LC 24 Fibers	LC 12 Fibers	SC 12 Fibers
OM3, 50/125	ICFC24ML1G	ICFC12ML1G	ICFC12MS1G
OM2, 50/125	ICFC24ML50	ICFC12ML50	ICFC12MS50
OM1, 62.5/125	ICFC24MLD6	ICFC12MLD6	ICFC12MSD6
OS1, 9/125	ICFC24SLD9	ICFC12SLD9	ICFC12SSD9



We offer tools to help remove connectors



Bend-insensitive fiber



Factory tested

# Fiber Optic Patch Cords



Dust caps are included for protection



LC



SC



ST



MPO

## Duplex Patch Cords, OFNR

- Lengths (zz\*) = 01, 02, 03, 05, 07, and 10 meters

	OM3 50/125	OM2 50/125	OM1 62.5/125	OS1 9/125
LC to LC	ICFOJ1G7zz*	ICFOJ1M7zz*	ICFOJ1M3zz*	ICFOJ1M5zz*
LC to SC	ICFOJ2G7zz*	ICFOJ2M7zz*	ICFOJ2M3zz*	ICFOJ2M5zz*
LC to ST	-	ICFOJ3M7zz*	ICFOJ3M3zz*	ICFOJ3M5zz*
SC to SC	ICFOJ8G7zz*	ICFOJ8C7zz*	ICFOJ8C3zz*	ICFOJ8C5zz*
SC to ST	-	ICFOJ9C7zz*	ICFOJ9C3zz*	ICFOJ9C5zz*
ST to ST	-	ICFOJ7C7zz*	ICFOJ7C3zz*	ICFOJ7C5zz*

## MPO Patch Cords, OFNP, 12 Fibers

- Lengths (zz\*) = 05, 10, 15, 20, 30, and 50 meters

OM3, 50/125	ICFOJATGzz*
OM2, 50/125	ICFOJATMzz*
OM1, 62.5/125	ICFOJATNzz*
OS1, 9/125	ICFOJATSzz*



# Racks & Cable Management



## Hinged Brackets

- Limited space/closet installations
- Available in EZ-Fold or traditional style
- Supports up to 60 lb. of equipment

## Open Frame Racks

- Limited floor space/small room installations
- Self-squaring design; easy to assemble
- Supports up to 125 lb. of equipment





## Enclosed Cabinets

- Small room/space for swing out
- For secure and non-secure installations
- Swings out to access equipment from the rear
- Supports up to 150 lb. of equipment



## Floor Racks

- Regulation size telecom rooms
- Available with 2 and 4 posts
- Supports up to 1500 lb. of equipment



# Racks



### Wall Mount Hinged Brackets, 6" Depth

- Up to 40 lb. capacity
- |               |            |
|---------------|------------|
| 1 RMS, 2-Pack | ICCMSHB1RC |
| 1 RMS         | ICCMSHB1RS |
| 2 RMS, 2-Pack | ICCMSHB2RC |
| 2 RMS         | ICCMSHB2RS |
| 4 RMS, 2-Pack | ICCMSHB4RC |
| 4 RMS         | ICCMSHB4RS |

### Wall Mount EZ-Fold Brackets, 15" Depth

- 30 lb. capacity
  - 2.5" height
  - Double mounting holes
  - No weight bears at the hinge
  - Patented
- |       |            |
|-------|------------|
| 2 RMS | ICCMSABRS2 |
| 4 RMS | ICCMSABRS4 |
| 6 RMS | ICCMSABRS6 |
| 8 RMS | ICCMSABRS8 |



### Wall Mount EZ-Fold Brackets, 6" Depth

- 30 lb. capacity
  - 2.5" height
  - Double mounting holes
  - No weight bears at the hinge
  - Patented
- |       |            |
|-------|------------|
| 2 RMS | ICCMSABR62 |
| 4 RMS | ICCMSABR64 |
| 6 RMS | ICCMSABR66 |
| 8 RMS | ICCMSABR68 |

### Wall Mount Vertical Hinged Brackets

- Up to 60 lb. capacity
  - Swings down 90°
- |                  |            |
|------------------|------------|
| 6 RMS, 12" Depth | ICCMSVHB06 |
| 8 RMS, 12" Depth | ICCMSVHB08 |
| 8 RMS, 18" Depth | ICCMSVHB18 |



### Wall Mount Racks, 18" Depth

- |                                    |        |            |
|------------------------------------|--------|------------|
| • 125 lb. capacity                 | 8 RMS  | ICCMSWMR08 |
| • Reinforced arms with 14 GA steel | 15 RMS | ICCMSWMR15 |
|                                    | 30 RMS | ICCMSWMR30 |



### Wall Mount Swing Frame Racks, 18" Depth

- |                                    |        |           |
|------------------------------------|--------|-----------|
| • 85 lb. capacity                  | 12 RMS | ICCMSFR12 |
| • Reversible installation          | 25 RMS | ICCMSFR25 |
| • Mounting screw template included |        |           |



### Wall Mount Enclosure Cabinets, 26" Depth

- |                                               |                        |            |
|-----------------------------------------------|------------------------|------------|
| • 150 lb. capacity                            | <b>Solid Door</b>      |            |
| • Vented side panels                          | 12 RMS                 | ICCMSWMC12 |
| • Knockouts on top and bottom for cable entry | 26 RMS                 | ICCMSWMC26 |
| • Reversible front door                       | <b>Plexiglass Door</b> |            |
|                                               | 12 RMS                 | ICCMSWMP12 |
|                                               | 26 RMS                 | ICCMSWMP26 |



### Wall Mount Utility Rack

- |                                     |       |            |
|-------------------------------------|-------|------------|
| • 75 lb. capacity                   | 5 RMS | ICCMSWMUR5 |
| • Mounts equipment vertically       |       |            |
| • Pre-assembled with swing out arms |       |            |



### 2-Post Distribution Racks

- Lightweight aluminum
- 19" EIA rack mount width
- 750 lb. capacity

7' H, 45 RMS  
6' H, 38 RMS  
4' H, 24 RMS  
Anchor Kit

ICCMSR1984  
ICCMSR1972  
ICCMSR1948  
ICCMSRFLKT



Adjustable depth

### Adjustable 4-Post Distribution Rack

- Adjustable depth: 27"-32"
- 19" EIA rack mount width
- 1500 lb. capacity

7' H, 45 RMS  
Anchor Kit

ICCMSR4P84  
ICCMSRFLKT



Cable channels

### Cable Management Rack






- 6" D x 3.15" W channels
- 19" EIA rack mount width
- 1000 lb. capacity

7' H, 44 RMS  
Anchor Kit

ICCMSMRH7  
ICCMSRFLKT



# Cable Managers



### Vertical Finger Duct Panels

#### Single-sided

**2-Pack, Side or Center Mount, Flat Bracket**

78" H x 6" W x 5" D ICCMSCMA73

**Side Mount, Flat Bracket**

78" H x 4" W x 5" D ICCMSCMA84

**Side Mount, Z-Bend Bracket**

78" H x 4" W x 5" D ICCMSCMA81

35" H x 4" W x 5" D ICCMSCMA21

#### Double-sided

**Center Mount, Z-Bend Bracket**

78" H x 4" W x 10" D ICCMSCMA82

35" H x 4" W x 10" D ICCMSCMA22

**Side Mount, Z-Bend Bracket**

78" H x 4" W x 10" D ICCMSCMA83

35" H x 4" W x 10" D ICCMSCMA23



### Vertical Channels with Plastic Covers 4-Pack ValuePack

- Mount on the front, rear, and in-between racks
- Front swivel latches
- Large rear openings
- Adjustable mounting brackets swing-out left and right
- One 4-pack can build two 7-foot channels

40" H, 4-Pack

ICCMSC40BK



### Single-sided Finger Ducts, 3" Depth

- |                           |               |            |
|---------------------------|---------------|------------|
| • 24 slotted ducts        | 1 RMS, 6-Pack | ICCMSCMAC1 |
| • Flexible fingers        | 1 RMS         | ICCMSCMA41 |
| • 16 GA steel frame       | 2 RMS, 6-Pack | ICCMSCMAC2 |
| • Includes slide-on cover | 2 RMS         | ICCMSCMA42 |



### Single-sided Finger Ducts, 5" Depth

- |                           |       |            |
|---------------------------|-------|------------|
| • 24 slotted ducts        | 1 RMS | ICCMSCMA15 |
| • Flexible fingers        | 2 RMS | ICCMSCMA25 |
| • 16 GA steel frame       |       |            |
| • Includes slide-on cover |       |            |



### Double-sided Finger Ducts

- |                           |               |            |
|---------------------------|---------------|------------|
| • 24 slotted ducts        | 1 RMS, 6-Pack | ICCMSCMAD1 |
| • Flexible fingers        | 1 RMS         | ICCMSCMA61 |
| • 16 GA steel frame       | 2 RMS, 6-Pack | ICCMSCMAD2 |
| • Includes slide-on cover | 2 RMS         | ICCMSCMA62 |



### Metal Blank Panels

- |                                    |                |            |
|------------------------------------|----------------|------------|
| • Fills open spaces between panels | 1 RMS, 12-Pack | ICCMSCMPC1 |
| • 16 GA steel frame                | 1 RMS          | ICCMSCMPB1 |
|                                    | 2 RMS, 12-Pack | ICCMSCMPC2 |
|                                    | 2 RMS          | ICCMSCMPB2 |
|                                    | 3 RMS, 6-Pack  | ICCMSCMPC3 |
|                                    | 3 RMS          | ICCMSCMPB3 |
|                                    | 4 RMS, 6-Pack  | ICCMSCMPC4 |
|                                    | 4 RMS          | ICCMSCMPB4 |





### Plastic Interbay Rings

- |                          |               |            |
|--------------------------|---------------|------------|
| • Five plastic rings     | 1 RMS, 6-Pack | ICCMSCMAV1 |
| • Rear cable openings    | 1 RMS         | ICCMSCMA51 |
| • 16 GA steel frame      | 2 RMS, 6-Pack | ICCMSCMAV2 |
| • Includes snap-on cover | 2 RMS         | ICCMSCMA52 |



### Extended Bracket 6-Pack ValuePack

- |                                  |             |           |
|----------------------------------|-------------|-----------|
| • Front or rear cable management | Front, 3" D | ICCMSCMC3 |
| • No extra RMS needed            | Rear, 5" D  | ICCMSCMC5 |
| • 16 GA steel frame              |             |           |



### Metal Vertical Rings

- |                                |               |            |
|--------------------------------|---------------|------------|
| • Five centered vertical rings | 1 RMS, 6-Pack | ICCMSCMP61 |
| • Horizontal management        | 1 RMS         | ICCMSCMPK1 |
| • 16 GA steel frame            | 2 RMS, 6-Pack | ICCMSCMP62 |
| • Includes steel snap-on cover | 2 RMS         | ICCMSCMPK2 |



### Metal Vertical and Horizontal Rings

- |                                                                 |                |                          |
|-----------------------------------------------------------------|----------------|--------------------------|
| • Three centered vertical rings with two outer horizontal rings | 1 RMS<br>2 RMS | ICCMSCMP31<br>ICCMSCMP32 |
| • Horizontal & vertical management                              |                |                          |
| • 16 GA steel frame                                             |                |                          |
| • Includes steel snap-on cover                                  |                |                          |



Wall mount



Ceiling mount



Batwing



Batwing clip

### J-Hooks 25-Pack ValuePacks

- Galvanized steel with a rust resistant zinc finish

#### Wall Mount

3/4" D	ICCMSJHK22
1 5/16" D	ICCMSJHK33
2" D	ICCMSJHK44
4" D	ICCMSJHK55

#### Ceiling Mount

3/4" D	ICCMSJH922
1 5/16" D	ICCMSJH933
2" D	ICCMSJH944
4" D	ICCMSJH955

#### Batwing

3/4" D	ICCMSJHW22
1 5/16" D	ICCMSJHW33
2" D	ICCMSJHW44
4" D	ICCMSJHW55



### Metal "L" Bracket

- Custom vertical or horizontal cable management
- 25-Pack ValuePack

0.95" H x 6" W

ICCMSCMPLC



### Vertical Metal Rings

- Mounts on the sides of racks
- Double-sided

3" W  
6" W

ICCMSCMPR3  
ICCMSCMPR4



### Vertical Metal Rings

- Mounts on the sides of racks
- 10-Pack ValuePack

1.70" W  
3" W

ICCMSCMPT1  
ICCMSCMPT2



### Cable Radius Manager

- Mounts on the side of brackets
- 20-Pack ValuePack

2.44" H x 3.6" W

ICCMSRMU1C



### Horizontal Plastic Ring

- Mounts on the sides of racks

10-Pack ValuePack  
Single, 1.25" H

ICCMSCMPV6  
ICCMSCMPR6



### Vertical Plastic Ring

- Mounts on the sides of racks

10-Pack ValuePack  
Single, 1.25" W

ICCMSCMPV5  
ICCMSCMPR5



### Universal Plastic Ring

- Mounts on the side or in-between two racks

10-Pack ValuePack  
Single, 3" H x 3" W

ICCMSCMPV7  
ICCMSCMPR7



### Metal Wall Mount D-Rings

- 100-Pack ValuePack

2" D  
3" D  
5" D

ICCMSDRM02  
ICCMSDRM03  
ICCMSDRM05



### Plastic Wall Mount D-Rings

- 100-Pack ValuePack

2" D  
3" D  
5" D

ICCMSDRP02  
ICCMSDRP03  
ICCMSDRP05



## Shelves



### Solid Bottom Rack Shelves

- Up to a 250 lb. capacity

#### Single-sided

10" D, 2 RMS, 2-Pack	ICCMSRSFC1
10" D, 2 RMS	ICCMSRSF10
15" D, 3 RMS, 2-Pack	ICCMSRSFC2
15" D, 3 RMS	ICCMSRSF15

#### Double-sided

20" D, 2 RMS, 2-Pack	ICCMSRDSC3
20" D, 2 RMS	ICCMSRDS20
30" D, 3 RMS	ICCMSRDS30
20" D, 3 RMS	ICCMSHDS20



### Vented Bottom Rack Shelves

- Up to a 100 lb. capacity

#### Single-sided

10" D, 2 RMS, 2-Pack	ICCMSRSVC1
10" D, 2 RMS	ICCMSRSV10
15" D, 3 RMS, 2-Pack	ICCMSRSVC2
15" D, 3 RMS	ICCMSRSV15

#### Double-sided

20" D, 2 RMS, 2-Pack	ICCMSRDVC4
20" D, 2 RMS	ICCMSRDV20
30" D, 3 RMS	ICCMSRDV30



### Adjustable 4-Post Shelf

- 125 lb. capacity

27"-32" D, 2 RMS	ICCMSRAS30
------------------	------------



### Vented 4-Post Shelf

- 125 lb. capacity

32" D, 2 RMS	ICCMSRFV32
--------------	------------



### Keyboard Rack Shelves

- 25 lb. capacity

#### Sliding Shelf

10" D, 3 RMS	ICCMSRKLST
--------------	------------

#### Sliding Mouse Tray

10" D, 3 RMS	ICCMSRKSMT
--------------	------------








### Wall Shelf

- 125 lb. capacity

17" D, 2-Pack	ICCMSWMSV2
---------------	------------



# Ladder Rack System



**Ladder Rack Kit**

- Includes a 5' runway, relay bracket, wall angle, and J-bolts

**Ladder Rack Runway**

- 16 GA steel with a durable powder-coated finish

**90° Flat Turn**

- Gradual sweeping bend

**90° Corner Turns**

- Routes cable vertically

Kit

ICCMSLRW05

7', 2-Pack ValuePack  
10'  
5'

ICCMSLSTV7  
ICCMSLST10  
ICCMSLST05

Flat Turn


ICCMSLFT90

Inside Turn  
Outside Turn


ICCMSLIR90  
ICCMSLOR90



Attach to side rail or rung



Radius Drop: tighten with one screw



### Radius Drops

- Maintains cable's bend radius at drop points

2-Pack ValuePack

ICCMSLRADB




### Cable Retainers

- Prevents cable from falling

10-Pack ValuePack

ICCMSLRARP





**Butt Splices**

- Joins ladder rack runway at ends

10-Pack ValuePack

ICCMSLRBSK

**Triangle Wall Support**

- Holds ladder rack runway to the wall, recommended every 5'

6-Pack ValuePack  
Single Support


ICCMSLTWS6  
ICCMSLTWSK

**Swivel Butt Splices**

- Allows ends to adjust to various angles

2-Pack ValuePack

ICCMSLESSK




### Wall Support Angle

- Mounts runway to the wall

2-Pack ValuePack  
Single Support Angle

ICCM SLAWS2  
ICCM SLAWSK



### Relay Rack Bracket

- Mounts and secures runway over 2-Post racks

ICCM SLRRBK




### 4-Post Relay Rack Brackets

- Secures runway over 4-Post racks

2-Pack ValuePack

ICCM SL4PBK




### 6' Threaded Ceiling Rods

- Ceiling mount to sustain over-hanging runway

2-Pack ValuePack

ICCM SLCMRK



### Wall Brackets

- Secures runway sections flat against the wall

2-Pack ValuePack

ICCM SLVWBK




### Floor Mount Feet

- Secure runway to the floor with mounting feet and butt splices

2-Pack ValuePack  
2-Pack ValuePack

ICCM SLMFFK  
ICCM SLMFF2



### Tee-Junction Splices

- Fastens runway in a tee intersection

2-Pack ValuePack

ICCM SLTJSK



### Protective End Caps

- Covers runway ends

2-Pack ValuePack

ICCM SLPECK



### J-Bolts

- Inserts over and secures runway

2-Pack ValuePack

ICCM SLJB01



# Residential Enclosures




## 14" Combo

- For small and single-family homes
- 20 GA steel
- UL Listed
- Designed to be stud mounted
- Also available in 21" and 28"

## 9" Combo

- For apartments and condos
- ABS plastic
- ETL Listed
- Designed to be surface or stud mounted




## 8" Combo


- For apartments and condos
- ABS plastic
- ETL Listed
- Designed to be surface or stud mounted

## Mini Combo

- For remodels and retrofits
- ABS plastic
- UL Listed
- Designed to be surface mounted



14" Net.Media Center



### 20 Gauge Steel Net.Media Center™ Combos

- For small and single-family homes
- Designed to be stud mounted
- Enclosures are compatible with most major brand modules

- 01** Hinged reversible door
- 02** Door latch
- 03** Lock knockout
- 04** 2" Cable knockouts
- 05** Rubber bumpers
- 06** Voice module

- 07** CAT 6 module
- 08** Video splitter module
- 09** Rubber grommets
- 10** Stud depth measurements
- 11** AC power knockouts
- 12** Extendable mounting tabs



21" Net.Media Center





28" Net.Media Center

	Voice Ports	Data Ports	Video Ports	Part No.
14"	8, RJ-31x	8, CAT 6	6, 2 GHz	ICRESDC14K
14"	8, RJ-31x	-	6, 2 GHz	ICRESDC14D
14"	6, RJ-31x	6, CAT 5e	-	ICRESDC14W
21"	8, RJ-31x	8, CAT 6	6, 2 GHz	ICRESDC21K
28"	8, RJ-31x	8, CAT 6	6, 2 GHz	ICRESDC28K



9" Net.Media Center




### ABS Plastic Net.Media Center™ Combos

- For apartments, condos, and remodels
- Designed to be surface or stud mounted
- 9" enclosures are compatible with most major brand modules


- 01 Cover
- 02 Pad lock hasp
- 03 Cable knockouts
- 04 Extendable mounting tabs
- 05 Screw-down cover holes
- 06 Voice module

- 07 Data module
- 08 Video splitter module
- 09 Plastic grommet
- 10 Stud depth measurements
- 11 AC power knockouts
- 12 Wiring diagram on cover





8" Net.Media Center



Mini Net.Media Center

	Voice Ports	Data Ports	Video Ports	Part No.
9"	8, RJ-31x	8, CAT 6	6, 2 GHz	ICRESDC9PK
9"	8, RJ-31x	-	6, 2 GHz	ICRESDC9PD
9"	6, RJ-31x	6, CAT 5e	-	ICRESDC9PW
8"*	8	-	6, 2 GHz	ICRDSMMBK8
8"*	6	6, CAT 5e	-	ICRDSMMBW8
Mini	8	8, CAT 5e	4, 2 GHz	ICRDSMMBK1
Mini	8	-	4, 1 GHz	ICRDSMMBD1
Mini	6	6, CAT 5e	-	ICRDSMMBW1

\* 8" Net.Media Centers are only available in 6-Pack ValuePack



### Voice Modules

- 8 Ports, bridged IDC
- Built-in RJ-31X and expansion ports

#### Voice Modules

PCB board, 10-Pack	ICRESVPA3D
PCB board	ICRESVPA3C
with plastic cover	ICRESVPA2C
with steel cover	ICRESVPA1C

#### Expansion Modules

PCB board	ICRESVPB3C
with plastic cover	ICRESVPB2C
with steel cover	ICRESVPB1C



### Data Modules

- 8 Ports, 110-Type IDC
- Supports up to 8 computers

#### CAT 6

PCB board, 10-Pack	ICRESDPB3D
PCB board	ICRESDPB3C
with plastic cover	ICRESDPB2C
with steel cover	ICRESDPB1C

#### CAT 5e

PCB board, 10-Pack	ICRESDPA3D
PCB board	ICRESDPA3C
with plastic cover	ICRESDPA2C
with steel cover	ICRESDPA1C



### Video Splitters

- Supports 2 GHz, 5~2300 MHz bandwidth
- Voice connectivity, 8-Ports, bridged IDC, supports up to 4 incoming phone lines and up to 8 extensions per line

1 x 4	ICRESAV42L
1 x 6	ICRESAV62L
1 x 6, 10-Pack	ICRESAV62V
1 x 8	ICRESAV82L

#### Video Splitter with Voice

1 x 4	ICRES8V42S
1 x 6	ICRES8V62S
1 x 8	ICRES8V82S



### Patch Panels

- Configurable with voice, data, and video modular connectors
- Lightweight metal bracket

6 HD Ports	ICRESBMP06
4 EZ® Ports	ICRESBMP04

### Net.Media Center Doors

- Replacement part
- Includes two thread forming screws for mounting to enclosure

28"	ICRESDR28H
21"	ICRESDR21H
14"	ICRESDR14H
9"	ICRESDR9PH



### Electronics Bracket

- Designed to hold electronics such as modems, routers, and switches
- Steel bracket

Bracket	ICRESDCBUM
---------	------------



### Cable Management Cover

- Designed to conceal cable
- Steel construction

Cover	ICRESCMC06
-------	------------



### Protective Grommets

- Install in enclosure knockouts to protect cable from damage
- 10 pieces per bag

Plastic Rubber	ICRESDCAC3
	ICRSDCAC2




### Door Lock and Keys

- Install on 14", 21", and 28" Net.Media Center doors
- Provides added security

Lock and two keys	ICRSDC2LK
-------------------	-----------



# Cords & Cable Assemblies



Enhanced strain relief



Snagless boot



50µ" gold plated

### Patch Cords

- Exceeds TIA-568 CAT 6A/6/5e performance standards
- Slim boot fits narrow port spacing
- Flexible snag-free strain relief boots maintain proper bend radius
- Factory tested and wired T568

#### 25-Pack ValuePacks

CAT 6 ICPCSDzzBL<sup>1</sup>

CAT 5e ICPCSCzzBL<sup>1</sup>

#### Single

CAT 6A FTP 10G ICPCSGzzxx<sup>2</sup>

CAT 6 ICPCSKzzxx<sup>3</sup>

CAT 5e ICPCSJzzxx<sup>3</sup>

#### Length (zz) & Color (xx) Options

zzBL<sup>1</sup> = 01, 03, 05, 07, 10'

zzxx<sup>2</sup> = 03, 05, 07, 10, 15, 25'

zzxx<sup>3</sup> = 01, 03, 05, 07, 10, 14, 25'



Shielded

### Modular Plugs 100-Pack ValuePack

- For customization of cords for voice or data applications
- UL Recognized

	Entry	Cable	AWG	Part No.
CAT 6	Oval	Solid/Stranded	23~24	ICMP8P8C6E
CAT 6/5e Shielded	Oval	Solid/Stranded	23~24	ICMP8P8C6S
CAT 5e	Oval	Stranded	24~26	ICMP8P8C5E
8P8C	Oval	Solid	24~28	ICMP8P8SRD
8P8C	Oval	Stranded	24~28	ICMP8P8CRD
8P8C	Flat	Stranded	24~28	ICMP8P8CFT



Solderless joints



Terminated IDC



Male



Female

### Telco Cables

- Provides connectivity for voice and low data applications
- 25-Pair, 24 AWG, UTP, RJ-21X

Male to Male	ICPCSTMMzz <sup>1</sup>
Female to Female	ICPCSTFFzz <sup>1</sup>
Female to Male	ICPCSTFMzz <sup>1</sup>
Male to Blunt	ICPCSTMBzz <sup>1</sup>
Female to Blunt	ICPCSTFBzz <sup>1</sup>

Length (zz<sup>1</sup>) = 05, 10, 15, 25'



Strap



Tape

### VELCRO® Cable Tie Strap ValuePacks


- Individually perforated
- One-piece fastening device
- Available in black
- 0.5" W

<b>Qwik Tie</b>	1120-Pack, 8" L	ICACSQV8BK
	112-Pack, 8" L	ICACSQB8BK
<b>ONE-WRAP®</b>	100-Pack, 8" L	ICACSVB8BK
	100-Pack, 12" L	ICACSVBTBK

### VELCRO® Cable Tie Tape

- 75' L x 0.5" W
- Cut to desired length

<b>Qwik Tie</b>	10-Roll Pack, Black	ICACSQVBK
	Single Roll, Black	ICACSQ75BK
<b>ONE-WRAP®</b>	Single Roll, Black	ICACSV75BK
	Single Roll, Blue	ICACSV75BL



### Nylon Cable Tie ValuePacks

- One-piece construction
- Flammability rating UL 94V-2
- MIL SPEC approved

100-Packs		
	Support	Part No.
4"	18 lb.	ICACSS04xx*
5.5"	18 lb.	ICACSS55BK
6"	40 lb.	ICACSM06xx*
12"	40 lb.	ICACSM12xx*
14.5"	50 lb.	ICACSL15xx*
14.5"	120 lb.	ICACSE15NL

1000-Packs		
	Support	Part No.
7.5"	50 lb.	ICACSL7Kxx*
8"	18 lb.	ICACSS8Kxx*
8.5"	40 lb.	ICACSM8Kxx*
11"	50 lb.	ICACSL1Kxx*

\*Color Options:






# Raceway & Wiring Ducts




Adhesive back



Available individually wrapped



One-piece design



01



02



03



04

**20-Pack ValuePacks**

- 6' Sections (per foot)<sup>1</sup>**  
 3/4" W, 1' L ICRWR11Sxx\*  
 1 1/4" W, 1' L ICRWR12Sxx\*  
 1 3/4" W, 1' L ICRWR13Sxx\*

- 8' Sections (per foot)<sup>1</sup>**  
 3/4" W, 1' L ICRWR118xx\*  
 1 1/4" W, 1' L ICRWR128xx\*  
 1 3/4" W, 1' L ICRWR138xx\*

**Individual Packaging**

- 6' Sections (per stick)**  
 3/4" W, 6' L ICRW22R6xx\*  
 1 1/4" W, 6' L ICRW33R6xx\*  
 1 3/4" W, 6' L ICRW44R6xx\*

- 8' Sections (per stick)**  
 3/4" W, 8' L ICRW22R8xx\*  
 1 1/4" W, 8' L ICRW33R8xx\*  
 1 3/4" W, 8' L ICRW44R8xx\*

<sup>1</sup>Cost is calculated per foot

**Outside Corner Covers**

- 10-Pack ValuePacks**  
 3/4" ICRW110Cxx\*  
 1 1/4" ICRW120Cxx\*  
 1 3/4" ICRW130Cxx\*

**Covers and Bases**

- 10-Pack ValuePacks**  
 3/4" ICRW110Bxx\*  
 1 1/4" ICRW120Bxx\*  
 1 3/4" ICRW130Bxx\*

**Inside Corner Covers**



- 10-Pack ValuePacks**  
 3/4" ICRW111Cxx\*  
 1 1/4" ICRW121Cxx\*  
 1 3/4" ICRW131Cxx\*

- Single**  
 3/4" ICRW22NCxx\*  
 1 1/4" ICRW33NCxx\*  
 1 3/4" ICRW44NCxx\*

**Tees**

- 10-Pack ValuePacks**  
 3/4" ICRW11TOxx\*  
 1 1/4" ICRW12TOxx\*  
 1 3/4" ICRW13TOxx\*


- Single**  
 3/4" ICRW22TExx\*  
 1 1/4" ICRW33TExx\*  
 1 3/4" ICRW44TExx\*

\*Color Options:    
 WH IV







Retail ready packaging



Three widths



Knockouts for raceway



05



06



07



08

### Ceiling Entries

#### 10-Pack ValuePacks

3/4"	ICRW11CExx*
1 1/4"	ICRW12CExx*
1 3/4"	ICRW13CExx*

#### Single

3/4"	ICRW22CMxx*
1 1/4"	ICRW33CMxx*
1 3/4"	ICRW44CMxx*

### Joint Covers

#### 10-Pack ValuePacks

3/4"	ICRW11JCxx*
1 1/4"	ICRW12JCxx*
1 3/4"	ICRW13JCxx*

#### Single

3/4"	ICRW22JCxx*
1 1/4"	ICRW33JCxx*
1 3/4"	ICRW44JCxx*

### 90° Flat Elbows

#### 10-Pack ValuePacks

3/4"	ICRW11EOxx*
1 1/4"	ICRW12EOxx*
1 3/4"	ICRW13EOxx*

#### Single

3/4"	ICRW22FExx*
1 1/4"	ICRW33FExx*
1 3/4"	ICRW44FExx*

### 90° Flat Elbows and Bases

#### 10-Pack ValuePacks

3/4"	ICRW11EBxx*
1 1/4"	ICRW12EBxx*
1 3/4"	ICRW13EBxx*

#### Single

3/4"	ICRW22EBxx*
1 1/4"	ICRW33EBxx*
1 3/4"	ICRW44EBxx*

### End Caps


#### 10-Pack ValuePacks

3/4"	ICRW11ECxx*
1 1/4"	ICRW12ECxx*
1 3/4"	ICRW13ECxx*

#### Single

3/4"	ICRW22ECxx*
1 1/4"	ICRW33ECxx*
1 3/4"	ICRW44ECxx*

\*Color Options:    
WH IV



### Wiring Ducts

- 2" W x 2" H
- Includes slide-on cover
- Cut, trim, and paint to fit any décor and application layout
- Pre-drilled mount holes

Slotted  
Solid

ICRWL226xx\*  
ICRWS226WH

\*Color Options:





# Tools & Accessories



### JackEasy™ Tool

- Cuts four pairs of wires
- Terminates with one squeeze
- 16 GA steel framework
- Works with HD and EZ® connectors

Tool  
Replacement blades

ICACSPDEH  
ICACS8WUEH



110 termination



66 termination



Blade storage


### 110 and 66 Single Blade Punch-Down Tool

- High and low impact settings
- Includes 110 and 66 blades

Tool ICACSPDT00

#### Replacement blades

110 blade ICACS110RB  
66 blade ICACS066RB



Seats 110 blocks



Replacement blade



Anti-slip grip

### 110 4-Pair Punch-Down Tool

- Cuts four pairs of wires
- 50 kgs impact force
- Anti-slip rubber grip

Tool ICACSPDT4P

Replacement blade ICACS04PH5



### Heavy Duty Modular Plug Crimping Tool

- Crimp 8-Position 8-Conductor modular plugs
- Ergonomic design provides a firm and comfortable grip


Tool ICACSCT845



### Universal Modular Plug Crimping Tool

- Crimp 4, 6, and 8-Position modular plugs

Tool ICACSCT864



### Universal Compression Tool

- Compress F-Type, RCA, BNC, and BNC 90° compression connectors and modular compression connectors
- Ergonomic design provides a firm and comfortable grip

Tool ICACSCT01U

#### F-Type Connectors 100-Packs

RG-6, compression ICRDSAV01C  
 RG-6Q, compression ICRDSAV04C  
 RG-59, compression ICRDSAV59C

#### F-Type Modular Connectors

RG-6Q, compression IC107FQGWH



### Economy Compression Tool


- Compress F-Type, RCA and BNC compression connectors

Tool

ICACSCT01E

#### F-Type Connectors 100-Packs

RG-6, compression ICRDSAV01C  
 RG-6Q, compression ICRDSAV04C  
 RG-59, compression ICRDSAV59C




### Handheld Termination Aid

- Works with HD and EZ modules
- Provides a base for termination

Aid

ICACSHTA01



### Stripper Tools

- Deluxe: UTP, STP, and coax cable
- Economy: UTP cable
- 5~6.2mm cable diameter

Deluxe  
Economy

ICACSTSUCD  
ICACSTSUS1




### Wire Cutter and Stripper

- Strips 12~24 AWG stranded wire and 10~22 AWG solid wire

Tool

ICACSCTRST



### Connector Removal Tool

- Removes modular keystone connectors in tight spaces
- Narrow profile head

Tool

ICACSP481

# Part Number Index

IC066BRCLP.....	34	IC107E5Cxx.....	07	IC110CMBWF.....	33
IC066CV050.....	34	IC107E5Vxx.....	07	IC110H1004.....	33
IC066DFT50.....	34	IC107F1Cxx.....	18	IC110HLDR.....	33
IC066NB050.....	34	IC107F01xx.....	18	IC110NF100.....	33
IC066NBC50.....	34	IC107F2Cxx.....	18	IC110PRK61.....	33
IC066SFT25.....	34	IC107F02xx.....	18	IC110RM100.....	33
IC106FP2xx.....	21	IC107F3Cxx.....	18	IC110RM200.....	33
IC107AHMWH.....	13	IC107F03xx.....	18	IC110RMCMB.....	33
IC107AS4VWH.....	21	IC107F4Cxx.....	18	IC110TC450.....	33
IC107AUSWH.....	15	IC107F04xx.....	18	IC110W1004.....	33
IC107B3Gxx.....	15	IC107F5Cxx.....	03	IC110W3004.....	33
IC107B5Fxx.....	15	IC107F5Vxx.....	03	IC110WF100.....	33
IC107B5Gxx.....	15	IC107F6Cxx.....	03	IC110WF300.....	33
IC107B8GWH.....	14	IC107F6Vxx.....	03	IC110WH100.....	33
IC107B9Fxx.....	15	IC107F06xx.....	18	IC110WK966.....	33
IC107B9Gxx.....	15	IC107F12xx.....	18	IC625S51xx.....	23
IC107BC1xx.....	22	IC107FD8xx.....	18	IC625S52xx.....	23
IC107BC2xx.....	22	IC107FFWSS.....	20	IC625SB8IV.....	24
IC107BE241.....	28	IC107FFWxx.....	20	IC625SV1IV.....	23
IC107BFCWH.....	15	IC107FM3xx.....	20	IC625SV2IV.....	23
IC107BFDWH.....	15	IC107FN4xx.....	20	IC630DA6SS.....	21
IC107BFGWH.....	14	IC107FQGWH.....	15, 88	IC630DB6xx.....	21
IC107BGCWH.....	15	IC107FT4xx.....	20	IC630DIBxx.....	17
IC107BGDWH.....	15	IC107HDMxx.....	13	IC630DSFxx.....	16
IC107BN0xx.....	11	IC107L6Cxx.....	07	IC630E6GWH.....	21
IC107BN2xx.....	11	IC107L6Vxx.....	07	IC630E60xx.....	21
IC107BNCxx.....	15	IC107LC2xx.....	11	IC630E66xx.....	21
IC107BNVxx.....	11	IC107LCGxx.....	11	IC630EB0xx.....	18
IC107BP8VB.....	32	IC107LF1xx.....	21	IC630EBDxx.....	18
IC107BP12V.....	32	IC107LF2xx.....	21	IC630EBSSS.....	20
IC107BP241.....	28	IC107LF3xx.....	21	IC630EG0xx.....	21
IC107BP481.....	28	IC107LF6xx.....	21	IC630EGGxx.....	21
IC107BP482.....	28	IC107MB6BK.....	24	IC635DS4xx.....	24
IC107C5CBK.....	10	IC107MRDxx.....	24	IC635DS8xx.....	24
IC107C5Exx.....	10	IC107MRSxx.....	24	IC640BDSxx.....	21
IC107C6Axx.....	10	IC107PMGWH.....	14	IC640BSSxx.....	21
IC107C6CBK.....	10	IC107PPS6A.....	29	IC1074Plxx.....	21
IC107C6Rxx.....	10	IC107PPU6A.....	29	IC1076F0xx.....	03
IC107C6Sxx.....	10	IC107R6GWH.....	14	IC1076FCxx.....	03
IC107CP6xx.....	10	IC107R8GWH.....	14	IC1076FVWH.....	03
IC107DA1xx.....	21	IC107RR5WH.....	14	IC1076V0xx.....	07
IC107DA2xx.....	21	IC107S01SS.....	20	IC1076VCxx.....	07
IC107DA4xx.....	21	IC107S01xx.....	20	IC1076VVWH.....	07
IC107DDHxx.....	13, 16	IC107S02SS.....	20	IC1078E5xx.....	07
IC107DFDSS.....	17	IC107S02xx.....	20	IC1078F5xx.....	03
IC107DFDxx.....	17	IC107S03SS.....	20	IC1078F6xx.....	03
IC107DFQWH.....	17	IC107S03xx.....	20	IC1078GAXxx.....	03
IC107DFSSS.....	17	IC107S04SS.....	20	IC1078L6xx.....	07
IC107DFSxx.....	17	IC107S04xx.....	20	IC1078S6A0.....	03
IC107DFTWH.....	17	IC107S06SS.....	20	IC06626P4C.....	34
IC107DH2xx.....	13, 16	IC107S06xx.....	20	IC06628P8C.....	34
IC107DI1xx.....	17	IC107SACWH.....	14	IC06686P6C.....	34
IC107DI2xx.....	17	IC107SAPxx.....	14	ICACS04PH5.....	87
IC107DI3xx.....	17	IC107SB1xx.....	22	ICACS8WUEH.....	86
IC107DI4xx.....	17	IC107SB2xx.....	22	ICACS066RB.....	87
IC107DI6xx.....	17	IC107SB4WH.....	22	ICACS110RB.....	87
IC107DPlxx.....	21	IC107SB6WH.....	22	ICACSCT01E.....	88
IC107DR2xx.....	16	IC107SBTxx.....	22	ICACSCT01U.....	88
IC107DR4xx.....	16	IC107SC2xx.....	11	ICACSCT845.....	88
IC107DSBxx.....	14	IC107SF1SS.....	20	ICACSCT864.....	88
IC107DSCxx.....	14	IC107SF2SS.....	20	ICACSCTRST.....	89
		IC107SF3SS.....	20	ICACSDCICL.....	31
		IC107SF4SS.....	20	ICACSDCVCL.....	31
		IC107SF6SS.....	20	ICACSE15NL.....	80
		IC107ST2xx.....	11	ICACSGK6AS.....	29
		IC107UAAWH.....	15	ICACSGKS00.....	29
		IC107UABWH.....	15	ICACSHTA01.....	89
		IC108SB1xx.....	23	ICACSL1Kxx.....	80
		IC108SB2xx.....	23	ICACSL7Kxx.....	80
		IC108SB4xx.....	23	ICACSL15xx.....	80
		IC108SB6xx.....	23	ICACSM06xx.....	80
		IC110CB4PC.....	33	ICACSM8Kxx.....	80
		IC110CB5PC.....	33	ICACSM12xx.....	80
		IC110CMBNF.....	33	ICACSMBDxx.....	24



ICACSMBSxx.....	24	ICCMSCMPK2.....	59	ICCMSRDVC4.....	63
ICACSPDT00.....	87	ICCMSCMPLC.....	61	ICCMSRFLKT.....	55
ICACSPDT4P.....	87	ICCMSCMPR3.....	61	ICCMSRFV32.....	63
ICACSPDTEH.....	86	ICCMSCMPR4.....	61	ICCMSRKLST.....	63
ICACSP481.....	89	ICCMSCMPR5.....	61	ICCMSRKSMT.....	63
ICACSQ75BK.....	80	ICCMSCMPR6.....	61	ICCMSRMU1C.....	61
ICACSQB8BK.....	80	ICCMSCMPR7.....	61	ICCMSRSF10.....	63
ICACSQV8BK.....	80	ICCMSCMPT1.....	61	ICCMSRSF15.....	63
ICACSQVKBK.....	80	ICCMSCMPT2.....	61	ICCMSRSFC1.....	63
ICACSS01BK.....	53-55	ICCMSCMPV5.....	61	ICCMSRSFC2.....	63
ICACSS04xx.....	80	ICCMSCMPV6.....	61	ICCMSRSV10.....	63
ICACSS8Kxx.....	80	ICCMSCMPV7.....	61	ICCMSRSV15.....	63
ICACSS55BK.....	80	ICCMSCMRH7.....	55	ICCMSRSVC1.....	63
ICACSTSUCD.....	89	ICCMSDRM02.....	61	ICCMSRSVC2.....	63
ICACSTSUS1.....	89	ICCMSDRM03.....	61	ICCMSSFR12.....	54
ICACSV75BK.....	80	ICCMSDRM05.....	61	ICCMSSFR25.....	54
ICACSV75BL.....	80	ICCMSDRP02.....	61	ICCMSVHB06.....	53
ICACSVB8BK.....	80	ICCMSDRP03.....	61	ICCMSVHB08.....	53
ICACSVBTBK.....	80	ICCMSDRP05.....	61	ICCMSVHB18.....	53
ICACSWDS10.....	34	ICCMSFCMC3.....	59	ICCMSWMC12.....	54
ICACSWDS20.....	34	ICCMSHB1RC.....	53	ICCMSWMC26.....	54
ICCABP5Exx.....	38	ICCMSHB1RS.....	53	ICCMSWMP12.....	54
ICCABP6Axx.....	38	ICCMSHB2RC.....	53	ICCMSWMP26.....	54
ICCABP6Exx.....	38	ICCMSHB2RS.....	53	ICCMSWMPR08.....	54
ICCABP6FBL.....	38	ICCMSHB4RC.....	53	ICCMSWMR15.....	54
ICCABP6Vxx.....	38	ICCMSHB4RS.....	53	ICCMSWMR30.....	54
ICCABR5Exx.....	38	ICCMSHDS20.....	63	ICCMSWMSV2.....	63
ICCABR6Axx.....	38	ICCMSJH922.....	60	ICCMSWMSUR5.....	54
ICCABR6Exx.....	38	ICCMSJH933.....	60	ICFC12ML1G.....	47
ICCABR6FBL.....	38	ICCMSJH944.....	60	ICFC12ML50.....	47
ICCABR6Vxx.....	38	ICCMSJH955.....	60	ICFC12MLD6.....	47
ICCMSABR62.....	53	ICCMSJHK22.....	60	ICFC12MS1G.....	47
ICCMSABR64.....	53	ICCMSJHK33.....	60	ICFC12MS50.....	47
ICCMSABR66.....	53	ICCMSJHK44.....	60	ICFC12MSD6.....	47
ICCMSABR68.....	53	ICCMSJHK55.....	60	ICFC12MSP5.....	46
ICCMSABRS2.....	53	ICCMSJHW22.....	60	ICFC12MSP6.....	46
ICCMSABRS4.....	53	ICCMSJHW33.....	60	ICFC12MSPG.....	46
ICCMSABRS6.....	53	ICCMSJHW44.....	60	ICFC12SLD9.....	47
ICCMSABRS8.....	53	ICCMSJHW55.....	60	ICFC12SSD9.....	47
ICCMSC40BK.....	57	ICCMSL4PBK.....	68	ICFC12SSP9.....	46
ICCMSCMA15.....	58	ICCMSLAWS2.....	68	ICFC24ML1G.....	47
ICCMSCMA21.....	57	ICCMSLAWSK.....	68	ICFC24ML50.....	47
ICCMSCMA22.....	57	ICCMSLCMRK.....	68	ICFC24MLD6.....	47
ICCMSCMA23.....	57	ICCMSLESK.....	67	ICFC24MLP5.....	46
ICCMSCMA25.....	58	ICCMSLFT90.....	65	ICFC24MLP6.....	46
ICCMSCMA41.....	58	ICCMSLIR90.....	65	ICFC24MLPG.....	46
ICCMSCMA42.....	58	ICCMSLJB01.....	68	ICFC24SLD9.....	47
ICCMSCMA51.....	59	ICCMSLMFF2.....	68	ICFC24SLP9.....	46
ICCMSCMA52.....	59	ICCMSLMFFK.....	68	ICFODE41WM.....	43
ICCMSCMA61.....	58	ICCMSLOR90.....	65	ICFOJ1G7zz.....	48
ICCMSCMA62.....	58	ICCMSLPECK.....	68	ICFOJ1M3zz.....	48
ICCMSCMA81.....	57	ICCMSLRBSP.....	67	ICFOJ1M5zz.....	48
ICCMSCMA82.....	57	ICCMSLRRCR.....	66	ICFOJ1M7zz.....	48
ICCMSCMA83.....	57	ICCMSLRRBK.....	68	ICFOJ2G7zz.....	48
ICCMSCMA84.....	57	ICCMSLRRDB.....	66	ICFOJ2M3zz.....	48
ICCMSCMAC1.....	58	ICCMSLRW05.....	65	ICFOJ2M5zz.....	48
ICCMSCMAC2.....	58	ICCMSLST05.....	65	ICFOJ2M7zz.....	48
ICCMSCMAD1.....	58	ICCMSLST10.....	65	ICFOJ3M3zz.....	48
ICCMSCMAD2.....	58	ICCMSLSTV7.....	65	ICFOJ3M5zz.....	48
ICCMSCMAV1.....	59	ICCMSLTJJK.....	68	ICFOJ3M7zz.....	48
ICCMSCMAV2.....	59	ICCMSLTWS6.....	67	ICFOJ7C3zz.....	48
ICCMSCMP31.....	59	ICCMSLTWSK.....	67	ICFOJ7C5zz.....	48
ICCMSCMP32.....	59	ICCMSLVWBK.....	68	ICFOJ7C7zz.....	48
ICCMSCMP61.....	59	ICCMSR4P84.....	55	ICFOJ8C3zz.....	48
ICCMSCMP62.....	59	ICCMSR1948.....	55	ICFOJ8C5zz.....	48
ICCMSCMPB1.....	58	ICCMSR1972.....	55	ICFOJ8C7zz.....	48
ICCMSCMPB2.....	58	ICCMSR1984.....	55	ICFOJ8G7zz.....	48
ICCMSCMPB3.....	58	ICCMSRAS30.....	63	ICFOJ9C3zz.....	48
ICCMSCMPB4.....	58	ICCMSRCMC5.....	59	ICFOJ9C5zz.....	48
ICCMSCMPC1.....	58	ICCMSRDS20.....	63	ICFOJ9C7zz.....	48
ICCMSCMPC2.....	58	ICCMSRDS30.....	63	ICFOJATGzz.....	48
ICCMSCMPC3.....	58	ICCMSRDS33.....	63	ICFOJATMzz.....	48
ICCMSCMPC4.....	58	ICCMSRDV20.....	63	ICFOJATNzz.....	48
ICCMSCMPK1.....	59	ICCMSRDV30.....	63	ICFOJATSzz.....	48

ICFOPB00BK.....	45	ICMPPMB606.....	24	ICRW11Cxx.....	82
ICFOPC16BK.....	45	ICMPPTF242.....	30	ICRW11JCxx.....	83
ICFOPC26BK.....	45	ICMPPTF244.....	30	ICRW11OBxx.....	82
ICFOPC161G.....	45	ICPCSCzzBL.....	78	ICRW11OCxx.....	82
ICFOPL16B5.....	45	ICPCSDzzBL.....	78	ICRW11TOxx.....	82
ICFOPL16BG.....	45	ICPCSGzzxx.....	78	ICRW12CExx.....	83
ICFOPL16BK.....	45	ICPCSJzzxx.....	78	ICRW12EBxx.....	83
ICFOPL161G.....	45	ICPCSKzzxx.....	78	ICRW12ECxx.....	83
ICFOPL1615.....	45	ICPCSTFBzz.....	79	ICRW12EOxx.....	83
ICFOPL1619.....	45	ICPCSTFFzz.....	79	ICRW12ICxx.....	82
ICFOPS16BK.....	45	ICPCSTFMzz.....	79	ICRW12JCxx.....	83
ICFOPS26BK.....	45	ICPCSTMBzz.....	79	ICRW12OBxx.....	82
ICFOPT16BK.....	45	ICPCSTMMzz.....	79	ICRW12OCxx.....	82
ICFOPT26BK.....	45	ICRDS0F5WH.....	19	ICRW12TOxx.....	82
ICFORE31RM.....	43	ICRDS0FLWH.....	19	ICRW13CExx.....	83
ICFORE62RM.....	43	ICRDS3RFWH.....	16	ICRW13EBxx.....	83
ICFORECAC2.....	43	ICRDSAV01C.....	88	ICRW13ECxx.....	83
ICFORECAC3.....	43	ICRDSAV04C.....	88	ICRW13EOxx.....	83
ICFORET4RM.....	43	ICRDSAV59C.....	88	ICRW13ICxx.....	82
ICFORPP1RM.....	44	ICRSDC2LK.....	76	ICRW13JCxx.....	83
ICFOSKFM12.....	43	ICRSDCAC2.....	76	ICRW13OBxx.....	82
ICFP96ML1G.....	44	ICRDSMMBD1.....	75	ICRW13OCxx.....	82
ICMA267D66.....	11	ICRDSMMBK1.....	75	ICRW13TOxx.....	82
ICMA350A6C.....	11	ICRDSMMBK8.....	75	ICRW22CMxx.....	83
ICMA3508DR.....	11	ICRDSMMBW1.....	75	ICRW22EBxx.....	83
ICMAGBLOCK.....	24	ICRDSMMBW8.....	75	ICRW22ECxx.....	83
ICMB89B0WH.....	34	ICRDSQBpxx.....	16	ICRW22FExx.....	83
ICMB89BCWH.....	34	ICRDSVOLWH.....	19	ICRW22JCxx.....	83
ICMP8P8C5E.....	78	ICRDSV05WH.....	19	ICRW22NCxx.....	82
ICMP8P8C6E.....	78	ICRDSVF5WH.....	19	ICRW22R6xx.....	82
ICMP8P8C6S.....	78	ICRDSVFLWH.....	19	ICRW22R8xx.....	82
ICMP8P8CFT.....	78	ICRES8V42S.....	76	ICRW22TExx.....	82
ICMP8P8CRD.....	78	ICRES8V62S.....	76	ICRW33CMxx.....	83
ICMP8P8SRD.....	78	ICRES8V82S.....	76	ICRW33EBxx.....	83
ICMPP12F5E.....	32	ICRESAV42L.....	76	ICRW33ECxx.....	83
ICMPP12F6E.....	32	ICRESAV62L.....	76	ICRW33FExx.....	83
ICMPP012U6.....	31	ICRESAV62V.....	76	ICRW33JCxx.....	83
ICMPP12V5E.....	31	ICRESAV82L.....	76	ICRW33NCxx.....	82
ICMPP12V60.....	31	ICRESBMP04.....	76	ICRW33R6xx.....	82
ICMPP24CP5.....	29	ICRESBMP06.....	76	ICRW33R8xx.....	82
ICMPP24CP6.....	29	ICRESCMC06.....	76	ICRW33TExx.....	82
ICMPP024T2.....	30	ICRESDC9PD.....	75	ICRW44CMxx.....	83
ICMPP24T2C.....	30	ICRESDC9PK.....	75	ICRW44EBxx.....	83
ICMPP024T4.....	30	ICRESDC9PW.....	75	ICRW44ECxx.....	83
ICMPP24T4C.....	30	ICRESDC14D.....	73	ICRW44FExx.....	83
ICMPP24TF2.....	30	ICRESDC14K.....	73	ICRW44JCxx.....	83
ICMPP24TF4.....	30	ICRESDC14W.....	73	ICRW44NCxx.....	82
ICMPP024U6.....	27	ICRESDC21K.....	73	ICRW44R6xx.....	82
ICMPP48C51.....	29	ICRESDC28K.....	73	ICRW44R8xx.....	82
ICMPP48C61.....	29	ICRESDCAC3.....	76	ICRW44TExx.....	82
ICMPP48CP5.....	29	ICRESDCBUM.....	76	ICRWL226xx.....	84
ICMPP48CP6.....	29	ICRESDPA1C.....	76	ICRWR11Sxx.....	82
ICMPP048T2.....	30	ICRESDPA2C.....	76	ICRWR12Sxx.....	82
ICMPP48T2C.....	30	ICRESDPA3C.....	76	ICRWR13Sxx.....	82
ICMPP048T4.....	30	ICRESDPA3D.....	76	ICRWR118xx.....	82
ICMPP48TF2.....	30	ICRESDPB1C.....	76	ICRWR128xx.....	82
ICMPP48TF4.....	30	ICRESDPB2C.....	76	ICRWR138xx.....	82
ICMPP048U6.....	27	ICRESDPB3C.....	76	ICRWS226WH.....	84
ICMPP125EV.....	31	ICRESDPB3D.....	76		
ICMPP0245E.....	27	ICRESDR9PH.....	76		
ICMPP245EV.....	27	ICRESDR14H.....	76		
ICMPP246AS.....	29	ICRESDR21H.....	76		
ICMPP246AU.....	29	ICRESDR28H.....	76		
ICMPP0246B.....	27	ICRESVPA1C.....	76		
ICMPP0485E.....	27	ICRESVPA2C.....	76		
ICMPP485EV.....	27	ICRESVPA3C.....	76		
ICMPP0486B.....	27	ICRESVPA3D.....	76		
ICMPP1260V.....	31	ICRESVPB1C.....	76		
ICMPP02460.....	27	ICRESVPB2C.....	76		
ICMPP2460V.....	27	ICRESVPB3C.....	76		
ICMPP04860.....	27	ICRW11CExx.....	83		
ICMPP4860V.....	27	ICRW11EBxx.....	83		
ICMPPICSxx.....	31	ICRW11ECxx.....	83		
ICMPPMB506.....	24	ICRW11EOxx.....	83		

# Success Stories



Elite Installers™ have won projects for:

- School districts
- University campuses
- Apartment complexes
- Medical hospitals
- Five-star hotels and resorts
- Government buildings
- Commercial buildings
- Retail stores
- Community centers
- Financial institutions
- And more!

Visit [icc.com/success](http://icc.com/success) to learn more.

# Commercial Residential



# Copper Fiber



# Structured Cabling Solutions



📍 2100 E Valencia Dr, Ste D Fullerton, CA 92831

🌐 [icc.com](http://icc.com)

☎ (888) ASK.4ICC (275.4422)

The information in this document is deemed to be reliable and accurate, but is subject to change without notice. ICC is not responsible for misprints, obsolete information, or errors.

MMILIT0448-18