

**Lamp Posts  
& Accessories**

**WAVE**  
LIGHTING

**WAVE**  
WAVE WAVE WAVE WAVE

877.870.WAVE (9283) • [www.wavelighting.com](http://www.wavelighting.com)

# Lamp Posts & Accessories

## DIRECT BURIAL RESIDENTIAL LAMP POSTS

- Fits Most Standard 3" Post Top Fixtures
- Textured Powdercoated Aluminum
- Crossarm Included Unless Otherwise Specified
- Includes Inlet Hole
- Made In The USA



**S11T**  
See page 10


POST LENGTH	SUGG. BURIAL DEPTH
7'	18"
8'	18"
10'	24"
12'	24"
14'	30"

### GUIDE: 295-320NCA-BK

**Dimensions:** O.D. = 2.950", I.D. = 2.850", Wall = .050"

ITEM #	OPTION	COLOR
295-7' Post	C-Conv. Outlet (338)	BK-Black
293-8' Post	320-Ezee Change Photo Control	WH-White
294-10' Post	NCA-No Crossarm	BZ-Bronze

**NOTE:** Crossarms available in black & white with gold balls, bronze posts ship with black crossarm. Posts with Crossarm, Photo Control, or Convenience Outlet come pre-punched for installation. Minor assembly required.




### BOLLARD & CUSTOM LENGTH POSTS (348) AVAILABLE ON Page 55

**BK-BLACK**

**WH-WHITE**

**BZ-BRONZE**



7'  
8'  
10'

7'  
8'  
10'

**SAFETY NOTE:** Selecting posts and electrical accessories for performance and safety requires a full understanding of various factors and conditions. Professional engineering assistance in selecting these items is highly recommended. Purchaser is responsible for meeting any and all codes or requirements. If you choose a post or electrical accessory without getting such assistance, you do so at your own risk.

**2420**  
Decorative Base  
See page 56



Specifications subject to change without notice.




## CAST ALUMINUM POST & BASE COMBINATION

- Fits Most Standard 3" Post Top Fixtures
- 2 Piece Snap Together System, No Tools Required
- Constructed of Sturdy Cast Aluminum
- Available in Black Only

### GUIDE: C6P2-BK

ITEM #	COLOR
C6P2-6'	BK-Black
C8P2-8'	
C10P2-10'	




Anchor Bolt 3/8" x 7"

6'

### C6P2-BK

**Post Dimensions:** O.D. = 3"  
I.D. = 2.8", Wall = .100", L = 6'

**Base Dimensions:**  
H = 21", W = 10 1/4"




Anchor Bolt 3/8" x 12"

8'

### C8P2-BK

**Post Dimensions:** O.D. = 3"  
I.D. = 2.8", Wall = .100", L = 8'

**Base Dimensions:**  
H = 28 1/2", W = 11 5/8"  
2"x4" Hand Hole



Anchor Bolt 3/8" x 12"

10'

### C10P2-BK

**Post Dimensions:** O.D. = 3"  
I.D. = 2.8", Wall = .100", L = 10'

**Base Dimensions:**  
H = 37", W = 16 5/8"  
2"x4" Hand Hole

**NOTE:** Includes anchor bolts and templates. Post and Base are two piece interlocking system that may ship separately.

**SAFETY NOTE:** Selecting posts for performance and safety requires a full understanding of various factors and conditions. Professional engineering assistance in selecting these items is highly recommended. Purchaser is responsible for meeting any and all codes or requirements. If you choose a post or electrical accessory without getting such assistance, you do so at your own risk.



Posts accommodate Photo Control 688. See page 55. Photo Controls sold separately.

Specifications subject to change without notice.

## DIRECT BURIAL ALUMINUM LAMP POSTS



### DIRECT BURIAL

Includes Inlet Hole

#### GUIDE: 2514-BK-320

**Post Dimensions:** O.D. = 2.950", Wall = .072"


ITEM #	COLOR	OPTION
2500-8'	BK-Black	C-Convenience Outlet
2510-10'	WH-White	320-Ezee Change Photo Control
2512-12'	BZ-Bronze	688-Button Photo Control
2514-14'		HH*-2"x4" Hand Hole

\*To meet U.L. and N.E.C. standards, any post designed to be mounted over 8' above ground includes a 2" x 4" (HH) Hand Hole and ground lug. 2512 & 2514 include Hand Hole unless otherwise specified.

### SEE PAGE 52 FOR .125" WALL DIRECT BURIAL OPTIONS

### DIRECT BURIAL

#### PUNCH LOCATIONS for 8', 10', & 12' Posts (Side View)




POST LENGTH	SUGG. BURIAL DEPTH
7'	18"
8'	18"
10'	24"
12'	24"
14'	30"

**SAFETY NOTE:** Selecting a post for performance and safety requires a full understanding of various factors and conditions. Professional engineering assistance in selecting a post is highly recommended.

Purchaser is responsible for meeting any and all codes or requirements. If you choose a post without getting such assistance, you do so at your own risk.

### DIRECT BURIAL

#### PUNCH LOCATIONS for 14' Posts (Side View)



Specifications subject to change without notice.



## SURFACE MOUNT ALUMINUM LAMP POSTS

### SURFACE MOUNT

Optional Flange Base & Cover

#### GUIDE: 2600-BZ

Post Dimensions: O.D. = 2.950", Wall = .072"

ITEM #	BASE TYPE	COLOR	OPTION
2600-8'	No Base or Cover	<b>BK</b> -Black	<b>C</b> -Conv. Outlet
2610-10'	<b>ST</b> -Standard Base	<b>BZ</b> -Bronze	<b>320</b> -Ezee Change Photo Control
2612-12'	<b>STV</b> -ST Base w/Cover	<b>WH</b> -White	<b>688</b> -Button Photo Control
	<b>HD</b> -Heavy Duty Base		<b>HH*</b> -2"x4" Hand Hole
	<b>HDV</b> -HD Base w/Cover		

\*To meet U.L. and N.E.C. standards, any post designed to be mounted over 8' above ground includes a 2" x 4" (**HH**) Hand Hole and ground lug. **2610** and **2612** include Hand Hole unless otherwise specified.

SEE PAGE 54 FOR COMPONENT OFFERINGS





2600-STV-BK



2600-HDV-BK

### SURFACE MOUNT

#### PUNCH LOCATIONS (Side View)



Anchor Bolt M8 x 12"



Spun Aluminum Base Cover for **ST** Base (2410)



Die Cast Aluminum Flange base with anchor bolts for up to 12' x 2.950" O.D. Posts

**ST-STANDARD BASE (2403)**


#### GUIDE: 2690-BZ-HH

Post Dimensions: O.D. = 2.950", Wall = .125"

ITEM #	BASE TYPE	COLOR	OPTION
2690-10'	No Base or Cover	<b>BK</b> -Black	<b>C</b> -Conv. Outlet
2692-12'	<b>ST</b> -Standard Base	<b>BZ</b> -Bronze	<b>320</b> -Ezee Change Photo Control
	<b>STV</b> -ST Base w/Cover	<b>WH</b> -White	<b>688</b> -Button Photo Control
	<b>HD</b> -Heavy Duty Base		<b>HH*</b> -2"x4" Hand Hole
	<b>HDV</b> -HD Base w/Cover		

\*To meet U.L. and N.E.C. standards, any post designed to be mounted over 8' above ground includes a 2" x 4" (**HH**) Hand Hole and ground lug. **2690** and **2692** include Hand Hole unless otherwise specified.

SEE PAGE 54 FOR COMPONENT OFFERINGS



Anchor Bolt 3/8" x 12"



Spun Aluminum Base Cover for **HD** Base (2411)



Heavy Duty Aluminum Flange base with anchor bolts for up to 14' x 2.950" O.D. Posts

**HD-HEAVY DUTY BASE (2405)**



Specifications subject to change without notice.

# Lamp Posts & Accessories

# 3" COMMERCIAL LAMP POSTS

## DIRECT BURIAL

Fits most 3" Post Top Fixtures  
Includes Inlet Hole



POST LENGTH	SUGG. BURIAL DEPTH
8'	18"
10'	24"
12'	24"
14'	30"

See Safety Note on page 53

## SURFACE MOUNTED

Welded Flange with Optional Decorative Cover. Anchor bolts included.  
Fits most 3" Post Top Fixtures



**NO COVER** **AB-AMERICANA** **DB-DECOR** **HX-HEXAGON** **RB-ROUND** **VB-VICTORIAN**  
2 PIECE COVER (3BC1) 2 PIECE COVER (3BC6) 2 PIECE COVER (3BC2) 1 PIECE COVER (3BC9) 2 PIECE COVER (3BC3)

### 3" ROUND ALUMINUM

.125 Wall Thickness

ITEM #	COLOR	OPTION
3588-8'	<b>BK-Black</b>	<b>C-Conv. Outlet</b>
3590-10'	<b>BZ-Bronze</b>	<b>320-Ezee Change</b>
3592-12'	<b>WH-White</b>	<b>Photo Control</b>
3594-14'		<b>688-Button Photo Control</b>
		<b>HH*</b>

### 3" FLUTED ALUMINUM

.125 Wall Thickness

ITEM #	COLOR	OPTION
3588F-8'	<b>BK-Black</b>	<b>688-Button Photo Control</b>
3590F-10'	<b>BZ-Bronze</b>	<b>HH*</b>
3592F-12'	<b>WH-White</b>	
3594F-14'		

### 3" ROUND ALUMINUM


.125 Wall Thickness

ITEM #	BASE TYPE	COLOR	OPTION
3688-8'	No Cover	<b>BK-Black</b>	<b>C-Conv. Outlet</b>
3690-10'	<b>AB-American</b>	<b>BZ-Bronze</b>	<b>320-Ezee Change</b>
3692-12'	<b>DB-Decor</b>	<b>WH-White</b>	<b>Photo Control</b>
	<b>HX-Hexagon</b>		<b>688-Button Photo Control</b>
	<b>RB-Round Cover</b>		<b>HH*</b>
	<b>VB-Victorian</b>		

### 3" FLUTED ALUMINUM

.125 Wall Thickness

ITEM #	BASE TYPE	COLOR	OPTION
3688F-8'	No Cover	<b>BK-Black</b>	<b>688-Photo Control</b>
3690F-10'	<b>AB-American</b>	<b>BZ-Bronze</b>	<b>HH*</b>
3692F-12'	<b>DB-Decor</b>	<b>WH-White</b>	
	<b>HX-Hexagon</b>		
	<b>RB-Round Cover</b>		
	<b>VB-Victorian</b>		





Round F-Fluted



3" Round 3" Fluted

PUNCH LOCATIONS (Side View)



Bolt Circle Pattern For 3" Posts  
Anchor Bolt 1/2" x 12"

\*To meet U.L. and N.E.C. standards, any post designed to be mounted over 8' above ground includes a 2" x 4" (HH) Hand Hole and ground lug. 3592, 3594, 3592F, 3594F, 3690, 3692, 3690F, and 3692F include Hand Hole unless otherwise specified.


Specifications subject to change without notice.

# 4" COMMERCIAL LAMP POSTS

# Lamp Posts & Accessories

## DIRECT BURIAL

Fits most 3" Post Top Fixtures  
Includes Inlet Hole



### SAFETY NOTES

All surface mount posts are supplied with welded mounting bases.

Selecting a post for performance and safety requires a full understanding of various factors and conditions. Professional engineering assistance in selecting a post is highly recommended. Purchaser is responsible for meeting any and all codes or requirements. If you choose a post without getting such assistance, you do so at your own risk.

**See Suggested Burial Depth on page 52**

### 4" ROUND ALUMINUM

.125 Wall Thickness

ITEM #	COLOR	OPTION
4590-10'	<b>BK-Black</b>	<b>HH*</b>
4592-12'	<b>BZ-Bronze</b>	
4594-14'	<b>WH-White</b>	

### 4" FLUTED ALUMINUM

.125 Wall Thickness

ITEM #	COLOR	OPTION
4590F-10'	<b>BK-Black</b>	<b>HH*</b>
4592F-12'	<b>BZ-Bronze</b>	
4594F-14'	<b>WH-White</b>	

## SURFACE MOUNTED

Welded Flange & 3" Tenon with Optional Decorative Cover. Anchor bolts included.  
Fits most 3" Post Top Fixtures



**NO COVER**



**AB-AMERICANA**  
2 PIECE COVER (4BC1)



**DB-DECOR**  
2 PIECE COVER (4BC6)



**RB-ROUND**  
1 PIECE COVER (4BC9)



**VB-VICTORIAN**  
2 PIECE COVER (4BC3)

### 4" ROUND ALUMINUM


.125 Wall Thickness

ITEM #	BASE TYPE	COLOR	OPTION
4688-8'	No Cover	<b>BK-Black</b>	<b>HH*</b>
4690-10'	<b>AB-American</b>	<b>BZ-Bronze</b>	
4692-12'	<b>DB-Decor</b>	<b>WH-White</b>	
4694-14'	<b>RB-Round Cover</b> <b>VB-Victorian</b>		


### 4" FLUTED ALUMINUM

.125 Wall Thickness


ITEM #	BASE TYPE	COLOR	OPTION
4688F-8'	No Cover	<b>BK-Black</b>	<b>HH*</b>
4690F-10'	<b>AB-American</b>	<b>BZ-Bronze</b>	
4692F-12'	<b>DB-Decor</b>	<b>WH-White</b>	
4694F-14'	<b>RB-Round Cover</b> <b>VB-Victorian</b>		



4" Round 4" Fluted



Bolt Circle Pattern For 4" Posts  
Anchor Bolt 3/4" x 18"



\*To meet U.L. and N.E.C. standards, any post designed to be mounted over 8' above ground includes a 2" x 4" (HH) Hand Hole and ground lug. 4592, 4594, 4592F, 4594F, 4690, 4692, 4694, 4690F, 4692F, and 4694F include Hand Hole unless otherwise specified.

Specifications subject to change without notice.



## CAST ALUMINUM & POLYCARBONATE POST TOP FITTERS

### Die Cast Aluminum

Medium Base Porcelain Socket, 4Kv Upon Request  
**Specify Option: (MG) Mogul Socket, (G) GU24 Socket**  
**Example: 1721-MG**



**1721** Black  
**1721B** Bronze  
**1720** White

For 10"-16" Globes and  
 11" x 17" Acorns with 5 1/4" Opening  
 Powdercoated Finish  
 I.D. = 3"



**1724** Black  
**1724B** BRONZE  
**1724W** White

For 18" Globes with 5 1/4" Opening  
 Powdercoated Finish  
 I.D. = 3"

### Polycarbonate

Medium Base Phenolic Socket  
**Specify Option: (G) GU24 Socket**  
**Example: 1721P-G**



**1721P** Black  
**1720P** White


For 10"-16" Globes with 5 1/4" Opening  
 I.D. = 3"



### MOUNTING HARDWARE INCLUDED


Consult factory when ordering replacement fitters for fixtures with options: Refractors, Cylinders, etc.

## FLANGE BASES & COVERS



**2403**

Die Cast Aluminum Flange base, Powdercoated Finish  
 Anchor Bolts Included, for 8' -12' x 2.950" O.D. Posts only  
**SPECIFY: Black, (B) Bronze, or (W) White**



**2405**

Heavy Duty Aluminum Flange base, Powdercoated Finish  
 Anchor Bolts Included, for up to 14' x 2.950" O.D. Posts  
**SPECIFY: Black, (B) Bronze, or (W) White**



**2410**

Spun Aluminum Base  
 Cover for **2403**  
 Powdercoated Finish  
**SPECIFY: Black,  
 (B) Bronze, or (W) White**



**2411**

Spun Aluminum Base  
 Cover for **2405**  
 Powdercoated Finish  
**SPECIFY: Black,  
 (B) Bronze, or (W) White**

### Slip-On Polymer Decorative Post Cover



**2420**

Polyethylene Decorative Slip On  
 Base Cover for Standard 3" Post  
 I.D. = 3"

**SPECIFY: (B) Black (W) White**  
 No Hardware Included



**NOTE:** It is REQUIRED that a (2405) Flange Base be used on any surface mount post that utilizes multiple H.I.D. Post Brackets. Allen Set Screws, 3/8" x 12" Zinc Plated Anchor Bolts, and Template are included with Flange Base. Flange Post Base sold separately.

Specifications subject to change without notice.



## POST FIXTURE ADAPTERS





**348**

3" Custom Length Post for use with **347** Surface Mount Adapter

**SPECIFY:**

Color: **(BK)** Black, **(WH)** White or **(BZ)** Bronze

Length: **(XX)** must be in 6" intervals  
Example Part Number: **348-12**



**347**

Pier Mount Adapter for use with **348** Stub Post

**SPECIFY:**

**(BK)** Black  
**(WH)** White  
**(BZ)** Bronze



**349**

Pier Mount Adapter for 3" Post Mount Fixtures

**SPECIFY:**

**(BK)** Black  
**(WH)** White  
**(BZ)** Bronze



**CP-689**

120V Photo Control (688 included) with Adaptor for 3" Posts

**SPECIFY:**

**(BK)** Black  
**(WH)** White

## POST ACCESSORIES




**335**

15" Aluminum Crossarm with Gold End Caps

3/4" Dia. mounting hole required


**SPECIFY:** Black or **(WH)** White



**HH**

2" x 4" Hand Hole Cover for 3" posts (includes mounting hardware)

**SPECIFY:** Black, **(B)** Bronze, or **(W)** White




**HH4**

2" x 4" Hand Hole Cover for 4" posts (includes mounting hardware)

**SPECIFY:** Black, **(B)** Bronze, or **(W)** White

## PHOTO CONTROLS & OUTLETS



**320**

120V for 3" Post with Ezee Change Plug, 1 3/8" Dia. mounting hole required  
Up to 300W Inc.,  
39W Fluor., 100W H.I.D.

**SPECIFY:** Black or **(W)** White



**688**

120V Button Photo Control  
1 1/16" Dia. mounting hole required  
Up to 300W Inc.,  
39W Fluor., 100W H.I.D.

**SPECIFY:** Black or **(W)** White



**338**

120V Grounded Convenience Outlet  
1 3/8" Dia. mounting hole required

**SPECIFY:** Black or **(W)** White

SEE SAFETY NOTE ON PAGE 48

Specifications subject to change without notice.

## CAST ALUMINUM BRACKETS



**WB5**

Contemporary Wall Bracket pre-wired w/20" pigtail for easy installation with 3" Post Mount Fixture. Max. Globe size: 16". I.D. = 3" H = 6", W = 4 1/2", E = 12 1/2" Powdercoated Finish  
**SPECIFY: (BK) Black (WH) White or (BZ) Bronze**



**PB5-CAP**

Cap for 3" Post I.D. = 3" Powdercoated Finish  
**SPECIFY: (BK) Black (WH) White or (BZ) Bronze**



**PB5**

Contemporary Wall Bracket pre-wired w/20" pigtail for easy installation with 3" Post Mount Fixture. PB5-CAP Included. Designed to mount to 3" Posts with minimum .125 wall thickness. Max. Globe size: 16". I.D. = 3" H = 9 1/2", W = 4 1/2", E = 16 1/2" Powdercoated Finish  
**SPECIFY: (BK) Black (WH) White or (BZ) Bronze**



**PB5-2**

Contemporary Wall Bracket pre-wired w/20" pigtail for easy installation with 3" Post Mount Fixture. PB5-CAP Included. Designed to mount to 3" Posts with minimum .125 wall thickness. Max. Globe size: 16". I.D. = 3" H = 9 1/2", W = 4 1/2", E = 29" Powdercoated Finish  
**SPECIFY: (BK) Black (WH) White or (BZ) Bronze**



**PB5-3**

Contemporary Wall Bracket pre-wired w/20" pigtail for easy installation with 3" Post Mount Fixture. Designed to mount to 3" Posts with minimum .125 wall thickness. Max. Globe size: 14". I.D. = 3" H = 9", W = 4 1/2", E = 29" Powdercoated Finish  
**SPECIFY: (BK) Black (WH) White or (BZ) Bronze**

See Safety Note on page 55

## CAST ALUMINUM FITTERS

4Kv Medium Base Porcelain Socket  
**Specify Option: (MG) Mogul Socket**



**1784**

Style A Cast Fitter for Globes & Acorns with 8" Neck  
H = 11", W = 10 1/4", I.D. = 3"



**1785**

Style B Fitter for Globes & Acorns with 8" Neck  
H = 10 1/2", W = 10 1/4", I.D. = 3"

Powdercoated Finish - **SPECIFY: (BK) Black, (BZ) Bronze or (WH) White**

## REFRACTORS



**1000135**

for Mogul Base Socket, Type V Distribution  
H = 6 5/8", Dia. = 6 1/8", Top I.D. = 5 1/4", Bottom I.D. = 3 1/4"


Type III



**1000137**

for Mogul Base Socket, Type III Distribution  
H = 6 5/8", Dia. = 6 1/8", Top I.D. = 5 1/4", Bottom I.D. = 3 1/4"

Type V



**1000138**

for Medium Base Socket, Type V Distribution  
H = 4 7/8", Dia. = 4 3/4", Top I.D. = 4", Bottom I.D. = 3"

## CAST ALUMINUM DECORATIVE BASE COVERS

### FOR MOST 3" DIAMETER POSTS

Decorative Base Covers come as a two piece system, and can be installed over existing Surface Mounted Posts. **3BC9** and **4BC9** are one piece system.



**3BC1**

Dia.: 13 1/8"  
Height: 24 1/8"



**3BC2**

Dia.: 11 1/2"  
Height: 13 5/8"



**3BC3**

Dia.: 11"  
Height: 26 3/8"



**3BC6**

Dia.: 11"  
Height: 9 5/8"



**3BC9**

Dia.: 10"  
Height: 3 1/2"  
Top I.D.: 4 1/8"



**4BC1**

Dia.: 15"  
Height: 27 5/8"



**4BC3**

Dia.: 12 1/8"  
Height: 29"



**4BC6**

Dia.: 12"  
Height: 9 5/8"



**4BC9**

Dia.: 11"  
Height: 3 1/2"  
Top I.D.: 5 3/8"

Powdercoated Finish - **SPECIFY: (BK) Black, (BZ) Bronze or (WH) White**


Posts sold separately.

Specifications subject to change without notice.

# RESIDENTIAL REPLACEMENTS




## LENSES & DIFFUSERS



**COLONIAL, SAXONY & VANGUARD  
COMPANION SIZE LANTERNS  
ACRYLIC**

\*144-Clear Beveled Diamond 145-Amber Beveled Diamond  
146-Clear Beveled 147-Frosted Beveled



**COMPANION SIZE  
EVERSTONE™ LANTERNS  
ACRYLIC**

1301724-Clear 1301725-Opal  
\*1301726-Frosted




**WALL PACK  
EVERSTONE™  
LANTERNS  
ACRYLIC**

\*1301727-Clear Prismatic  
1301728-Opal



**VICTORIAN  
LANTERN  
ACRYLIC**

\*1300371-Opal  
1300372-Black



**COLONIAL, SAXONY & VANGUARD  
FULL SIZE LANTERNS  
ACRYLIC**

148-Clear Beveled 149-Frosted Beveled  
\*153-Amber Beveled Diamond 154-Clear Beveled Diamond



**FULL SIZE  
EVERSTONE™ LANTERNS  
ACRYLIC**

1301733-Clear 1301734-Frosted  
\*1301735-Opal



**LANTERN  
CHIMNEY  
GLASS**

\*1300316-Frosted



**VICTORIAN  
LANTERN  
ACRYLIC**

\*1300373-Clear Lens  
with Trim Ring (sold assembled)

## GLOBES & ACORNS W/5 1/4" NECKLESS OPENING



**CLEAR  
POLYCARBONATE**  
1256-12"  
1456-14"  
1656-16"  
1856-18"

**ACRYLIC**  
1066-10"  
1266-12"  
1466-14"  
1666-16"  
1866-18"



**OPAL  
POLYCARBONATE**  
1255-12"  
1455-14"  
1655-16"  
1855-18"

**ACRYLIC**  
1065-10"  
1265-12"  
1465-14"  
1665-16"  
1865-18"



**SMOKE  
POLYCARBONATE**  
1258-12"  
1458-14"  
1658-16"  
1858-18"

**ACRYLIC**  
1068-10"  
1268-12"  
1468-14"  
1668-16"  
1868-18"



**CLEAR PRISMATIC  
POLYCARBONATE**  
1859-18"  
  
**ACRYLIC**  
1069-10"  
1269-12"  
1669-16"  
1869-18"



**CLEAR TEXTURED  
POLYCARBONATE**  
1756-For 2017CL  
**ACRYLIC**  
1766-For 8017CL

**OPAL TEXTURED  
POLYETHYLENE**  
1776-For 9017



**CLEAR TEXTURED  
POLYCARBONATE**  
2067-For 2018CL  
**ACRYLIC**  
2057-For 8018CL

**OPAL TEXTURED  
POLYETHYLENE**  
2077-For 9018

## GLOBES & ACORNS W/4" FITTER NECK



**ACRYLIC**  
0800407-8" Clear  
0800408-8" Opal



**ACRYLIC**  
0800411-12" Clear  
0800410-12" Opal



**CLEAR TEXTURED  
POLYCARBONATE**  
1467-For S27S/T

## SUGGESTED MAX WATTAGES

SIZE	ACRYLIC			POLYCARBONATE			POLYETHYLENE		
	INC.	FLUOR.	H.I.D.	INC.	FLUOR.	H.I.D.	INC.	FLUOR.	H.I.D.
10"	75W	18W	--	--	18W	--	--	--	--
12"	100W	26W	--	100W	26W	--	--	--	--
14"	150W	32W	--	150W	32W	--	--	--	--
16"	150W	32W	70W	150W	32W	70W	--	--	--
18"	150W	32W	100W	150W	32W	100W	--	--	--
<b>ACORNS</b>	<b>INC.</b>	<b>FLUOR.</b>	<b>H.I.D.</b>	<b>INC.</b>	<b>FLUOR.</b>	<b>H.I.D.</b>	<b>INC.</b>	<b>FLUOR.</b>	<b>H.I.D.</b>
1756	--	--	--	150W	32W	70W	--	--	--
2067	--	--	--	150W	32W	70W	--	--	--


Suggested Max Wattages is for use as a general reference chart only. No warranty or guarantee is expressed or implied, as product suitability is determined by installation.

Specifications subject to change without notice.


# COMMERCIAL REPLACEMENTS




## ACRYLIC LENSES




**C31T LANTERNS**  
**ACRYLIC**  
**C31TL-LENS**-Opal  
**C31TP-LENS**-Prismatic




**C32T LANTERNS**  
**ACRYLIC**  
**C32TL-LENS**-Opal  
**C32TP-LENS**-Prismatic




**C33T LANTERNS**  
**ACRYLIC**  
**C33TL-LENS**-Opal  
**C33TP-LENS**-Prismatic




**C34T & C35T LANTERNS**  
**ACRYLIC**  
**C34TF-LENS**-Frosted



**C36T LANTERNS**  
**ACRYLIC**  
**C36TC-LENS**-Clear  
**C36TL-LENS**-Opal



**C37T LANTERNS**  
**ACRYLIC**  
**C37TC-LENS**-Clear  
**C37TL-LENS**-Opal



**C59T LANTERNS**  
**ACRYLIC**  
**C59TF-LENS**-Frosted

## 8" FITTER NECK OPENING GLOBES

24", 27", 30" & 36" Globes Available  
Contact Sales with Questions



**CLEAR**

**POLYCARBONATE**  
**1856-8N**-18"  
**2056-8N**-20"

**ACRYLIC**  
**1866-8N**-18"  
**2066-8N**-20"



**OPAL**

**POLYCARBONATE**  
**1855-8N**-18"  
**2055-8N**-20"

**ACRYLIC**  
**1865-8N**-18"  
**2065-8N**-20"



**SMOKE**

**POLYCARBONATE**  
**1858-8N**-18"  
**2058-8N**-20"

**ACRYLIC**  
**1868-8N**-18"  
**2068-8N**-20"



**CLEAR PRISMATIC**

**POLYCARBONATE**  
**1859-8N**-18"  
**2059-8N**-20"

**ACRYLIC**  
**1869-8N**-18"  
**2069-8N**-20"

### SUGGESTED MAX WATTAGES

SIZE	ACRYLIC		POLYCARBONATE	
	INC.	H.I.D.	INC.	H.I.D.
18"	150W	100W	150W	250W
20"	150W	150W	150W	250W
ACORNS	INC.	H.I.D.	INC.	H.I.D.
0801390	--	--	150W	250W
0801391	--	--	150W	250W
0801392	--	--	150W	250W
3467	--	--	150W	250W

Suggested Max Wattages is for use as a general reference chart only. No warranty or guarantee is expressed or implied, as product suitability is determined by installation.

## 8" FITTER NECK OPENING ACORNS



**CLEAR TEXTURED**  
**POLYCARBONATE**  
**3467**

Acorn with 8" Necked Opening for C75TC and C76TC Fixtures



**CLEAR TEXTURED**  
**POLYCARBONATE**  
**0801390\***

Acorn with 8" Necked Opening for C83TC and C84TC Fixtures\*\*



**CLEAR TEXTURED**  
**POLYCARBONATE**  
**0801391\***

Acorn with 8" Necked Opening for C85TF and C86TF Fixtures\*\*



**CLEAR TEXTURED**  
**POLYCARBONATE**  
**0801392\***

Acorn with 8" Necked Opening for C77TF and C78TF Fixtures

\* For Finial - **SPECIFY: (DR)** Drill Hole

\*\* For Hood - **SPECIFY: (TR)** Trim Top For C91 and C92, **(TR2)** Trim Top For C93 and C94

**Contact Sales for Acrylic Acorns in Clear, Opal & Frost**

Specifications subject to change without notice.