

PROGRESS[®]
LIGHTING



PRODUCT
SUPPLEMENT
JANUARY 2016





CONTENTS

Families	2
Chandelier Additions . . .	70
Pendants	78
Close-to-Ceiling	83
Sconces	92
Bath & Vanity	93
Outdoor	112
Security	136
LED Surface Mount . . .	137
Recessed	138
Step Lights	140
Lamps	141
Accessories	141
Index	144



ELINA

THREE-LIGHT SEMI-FLUSH

P3672-104 Polished Nickel
Stem and ceiling mounts both included. Includes one 6" stem, two 12" stems and 6 links of chain.
Size: 18" dia., 13" ht. Overall ht. w/stem 55"; wire 12'.
Lamps: Three medium base lamps, each 100w max.



FOUR-LIGHT PENDANT

P3987-104 Polished Nickel
Size: 16" dia., 17-3/4" ht. Overall ht. w/stem 94"; wire 15'.
Lamps: Four medium base lamps, each 100w max.

P4733-104



SEVEN-LIGHT CHANDELIER

P4733-104 Polished Nickel
Size: 32" dia., 32" ht. Overall ht. w/stem 98"; wire 15'.
Lamps: Seven medium base lamps, each 100w max.



All Elina stem-hung fixtures shown here include one 6" stem, four 12" stems and 6 links of chain unless noted.

For additional Elina fixtures see Catalog 131.

ELINA SPINS A TRADITIONAL CLASSIC AND MODERN FORM BY EXAGGERATING HEIRLOOM QUALITY DETAILS. TALL, TRUMPETED OPAL GLASS AND A POLISHED NICKEL FINISH CREATE A DISTINCTIVE SILHOUETTE.



TWO-LIGHT BATH
P2173-104 Polished Nickel
 Size: 13-3/4" W., 10-1/4" ht.
 Extends 6-3/8". H/CTR 4".
 Lamps: Two medium base lamps, each 100w max.

FOUR-LIGHT BATH
P2174-104 Polished Nickel
 Size: 32-1/4" W., 10-1/4" ht.
 Extends 6-3/8". H/CTR 4".
 Lamps: Four medium base lamps, each 100w max.

MINI-PENDANT
P5606-104 Polished Nickel
 Size: 4-3/8" dia., 9-3/4" ht.
 Overall ht. w/stem 76"; wire 10'.
 Lamp: One medium base lamp, 100w max.



P2174-104

Bath fixtures mount up or down.

ESTEEM'S EXAGGERATED CLASSIC FRAME OFFERS CASUAL LUX STYLING FOR THE HOME. OVERSIZED SINGLE TIERED CHANDELIERS WITH K9 FINIAL ACCENTS. THE FOYER PENDANT FEATURES A FRAMELESS DESIGN, CREATING A FLOATING EFFECT FOR THIS ELEGANT FIXTURE.

ESTEEM



FIVE-LIGHT CHANDELIER
P4615-20 Antique Bronze
Size: 27" dia., 27" ht. Overall ht. w/chain 102"; wire 15'.
Lamps: Five candelabra base lamps, each 60w max.

SEVEN-LIGHT CHANDELIER
P4616-20 Antique Bronze
Size: 34" dia., 27" ht. Overall ht. w/chain 102"; wire 15'.
Lamps: Seven candelabra base lamps, each 60w max.

FOUR-LIGHT PENDANT
P5120-20 Antique Bronze
Size: 14" dia., 21-1/4" ht. Overall ht. w/chain 87"; wire 15'.
Lamps: Four candelabra base lamps, each 60w max.

ONE-LIGHT WALL SCONCE
P7174-20 Antique Bronze
Size: 5-3/4" W., 12-3/4" ht. Extends 8". H/CTR 7-1/2".
Lamp: One candelabra base lamp, 60w max.



Harmony

HARMONY'S FIXTURES – CHARACTERIZED BY GEOMETRIC FRAMES AND FABRIC SHADES – ARE NOW AVAILABLE IN A BRUSHED NICKEL FINISH.



P3530-09

P3530-09
shown close-to-ceiling



P3531-09

P3531-09
shown close-to-ceiling



P3529-09



P3529-09
shown close-to-ceiling



THREE-LIGHT CONVERTIBLE

P3529-09 Brushed Nickel
Size: 12-3/4" dia., 10-1/4" ht.
Overall ht. w/stem 77"; wire 12'.
Lamps: Three medium base lamps, each 75w max.

THREE-LIGHT CONVERTIBLE

P3530-09 Brushed Nickel
Size: 15" dia., 10-1/2" ht. Overall ht. w/stem 77"; wire 12'.
Lamps: Three medium base lamps, each 100w max.

THREE-LIGHT CONVERTIBLE

P3531-09 Brushed Nickel
Size: 18" dia., 11-1/4" ht. Overall ht. w/stem 78"; wire 12'.
Lamps: Three medium base lamps, each 100w max.

All Harmony stem-hung fixtures shown here include one 6" stem, four 12" stems and 6 links of chain.

Draper



Shown: P4719-104 chandelier with P2101-104 bath bracket.

All fixtures on this spread are shown with P7826-01 vintage lamps.

WITH CHARM AND INTRIGUE, NEW OPTIONS IN THE DRAPER FAMILY ARE INSPIRED BY MID-CENTURY CLASSIC DESIGNS.

TO ADD A GREATER DESIGN EFFECT, SELECT EITHER TUBULAR OR GLOBE STYLE LAMPS TO CREATE A TRULY SIGNATURE STATEMENT FOR YOUR HOME.

FOR ADDED VERSATILITY, THE ANTIQUE BRONZE FIXTURES INCLUDE TWO FINIAL OPTIONS – NATURAL BRASS AND ANTIQUE BRONZE.

FIVE-LIGHT CHANDELIER

P4718-20 Antique Bronze

P4718-104 Polished Nickel

Size: 25" dia., 15-5/8" ht. Overall
ht. w/chain 82"; wire 15'.

Lamps: Five candelabra base
lamps, each 60w max.



All Draper hanging fixtures
include one 6" stem, four 12"
stems and 6 links of chain.

Draper



THREE-LIGHT CHANDELIER

P4717-20 Antique Bronze

P4717-104 Polished Nickel

Size: 13" dia., 16-1/4" ht. Overall
ht. w/chain 82-1/4"; wire 15'.

Lamps: Three candelabra base
lamps, each 60w max.

MINI-PENDANT

P5061-20 Antique Bronze

P5061-104 Polished Nickel

Size: 6-1/2" dia., 12-1/4" ht.

Overall ht. w/chain 78"; wire 10'.

Lamp: One candelabra base
lamp, 60w max.



All fixtures on this spread are shown
with P7826-01 vintage lamps.

WITH CHARM AND INTRIGUE, NEW OPTIONS IN THE DRAPER FAMILY ARE INSPIRED BY MID-CENTURY MODERN CLASSIC DESIGNS.

TO ADD A GREATER DESIGN EFFECT, SELECT EITHER TUBULAR OR GLOBE STYLE LAMPS TO CREATE A TRULY SIGNATURE STATEMENT FOR YOUR HOME.

NINE-LIGHT CHANDELIER

P4719-20 Antique Bronze

P4719-104 Polished Nickel

Two-tier.

Size: 32" dia., 21-3/4" ht. Overall ht. w/chain 88"; wire 15'.

Lamps: Nine candelabra base lamps, each 60w max.

P4719-20
shown with bronze
finials



P4719-104



All Draper hanging fixtures include one 6" stem, four 12" stems and 6 links of chain.

Swing



P7159-20
shown with P7825-01 lamp

WALL SCONCE

P7159-20 Antique Bronze
Natural brass backplate.
Size: 11-3/4" W., 11-3/4" ht.
Extends 4". H/CTR 5-7/8".
Lamp: One medium base lamp,
60w max.




Shown: P4744-20 chandelier with P7825-01 vintage lamps and P2101 sconce with P7826-01 vintage lamp.

For additional Swing fixtures see Catalog 131.



P5180-20
shown with
P7827-01 vintage lamps

NEW ADDITIONS TO THIS POPULAR VINTAGE ELECTRIC FAMILY. SPHERICAL PENDANTS WITHIN SWING FEATURES MIXED METAL ACCENTS. AND VINTAGE UNDERTONES. WALL SCONCE FEATURES NATURAL BRASS BACKPLATE.



P5150-20
shown with
P7825-01 vintage lamps

FOUR-LIGHT PENDANT

P5150-20 Antique Bronze
Size: 20" dia., 11-3/4" ht. Overall
ht. w/chain 87"; wire 15'.
Lamps: Four medium base
lamps, each 100w max.



P5190-20
shown with
P7827-01 vintage lamps

ONE-LIGHT SMALL PENDANT

P5180-20 Antique Bronze
Size: 14" dia., 23-1/4" ht. Overall
ht. w/chain 92-1/2"; wire 12'.
Lamp: One medium base lamp,
60w max.

FOUR-LIGHT MEDIUM PENDANT

P5190-20 Antique Bronze
Size: 20" dia., 23-1/4" ht. Overall
ht. w/chain 98-1/2"; wire 15'.
Lamps: Four medium base
lamps, each 60w max.

FOUR-LIGHT LARGE PENDANT

P5191-20 Antique Bronze
Size: 25" dia., 28-1/4" ht. Overall
ht. w/chain 102"; wire 15'.
Lamps: Four medium base
lamps, each 60w max.



P5191-20
shown with
P7827-01 vintage lamps

Trestle



Shown: P5168-71 pendants with P7825-01 vintage lamps.

FIXTURES WITHIN THE TRESTLE COLLECTION OFFER A HANDSOME LOOK FOR INDUSTRIAL OR RUSTIC LIVING SPACES. THE GILDED IRON FINISH IS ENHANCED BY HAND-PAINTED GOLDEN OAK ACCENTS.

FOUR-LIGHT LINEAR CHANDELIER


P4720-71 Gilded Iron with hand-painted golden oak accents
Size: 32-1/2" L., 15" W., 20-3/8" ht.
Overall ht. w/chain 95"; wire 15'.
Lamps: Four medium base lamps, each 60w max.

ONE-LIGHT PENDANT

P5152-71 Gilded Iron with hand-painted golden oak accents
Size: 14" dia., 8-3/4" ht. Overall ht. w/chain 72"; wire 10'.
Lamp: One medium base lamp, 60w max.


FOUR-LIGHT PENDANT

P5168-71 Gilded Iron with hand-painted golden oak accents
Size: 20" dia., 17" ht. Overall ht. w/stem 92"; wire 15'.
Lamps: Four medium base lamps, each 60w max.



All fixtures on this page shown with P7825-01 vintage lamps.

Marque



Shown: P3598-20 foyer fixture

MAKING A DISTINCT MARK ON TODAY'S INTERIORS, THIS NEW FASHION PENDANT COLLECTION EXUDES A CHIC SOPHISTICATION.

WITH ANTIQUE TEXTURED GLASS AND AN ANTIQUE BRONZE FRAME, THIS VINTAGE PENDANT FAMILY CAN BE USED AS A SLEEK SUBSTITUTE FOR CHANDELIERS IN A VARIETY OF LIVING SPACES, INCLUDING FOYERS AND HALLWAYS.

ONE-LIGHT FOYER

P3598-20 Antique Bronze
Size: 12" dia., 19-3/4" ht. Overall
ht. w/stem 86"; wire 15'.
Lamp: One medium base lamp,
100w max.

THREE-LIGHT FOYER

P3601-20 Antique Bronze
Size: 18" dia., 28-3/4" ht. Overall
ht. w/stem 95"; wire 15'.
Lamps: Three medium base
lamps, each 100w max.

MINI-PENDANT

P5073-20 Antique Bronze
Size: 7-3/4" dia., 9-1/4" ht.
Overall ht. w/stem 75-1/4";
wire 10'.
Lamp: One medium base
lamp, 100w max.



*All Marque stem-hung fixtures
include one 6" stem, four 12"
stems and 6 links of chain.*

COLLINS EMBRACES THE TREND TOWARDS STYLING WITH PENDANTS AS THE PRIMARY FIXTURE. THE WATER GLASS GALLERY CONTAINS BOTH RUSTIC AND MODERN UNDERTONES, WHILE A MICA SHADE PROVIDES RICH, GLIMMERING LIGHT.

Collins



ONE-LIGHT PENDANT

P5102-20 Antique Bronze
Size: 12" dia., 14" ht.
Overall ht. w/chain 80"; wire 10'.
Lamp: One medium base lamp, 100w max.

ONE-LIGHT PENDANT

P5115-20 Antique Bronze
Size: 17" dia., 20" ht.
Overall ht. w/chain 86"; wire 10'.
Lamp: One medium base lamp, 100w max.



All stem-hung fixtures shown on this spread include one 6" stem, four 12" stems and 6 links of chain.

Cirrine

CIRRINE APPEALS TO THE CREATIVE SPIRIT WITHIN ALL OF US. HAND FORMED ARCHING ELEMENTS ARE HIGHLIGHTED BY A PAINTED FINISH THAT FEATHERS FROM A RICH BRONZE TONE TO A VINTAGE BRASS ACCENT. ETCHED WHITE GLASS COMPLEMENTS THE ARTISTIC FRAME.

THREE-LIGHT CHANDELIER

P4699-20 Antique Bronze
Size: 18" dia., 13-1/2" ht.
Overall ht. w/stem 79"; wire 15'.
Lamps: Three medium base lamps, each 100w max.

FIVE-LIGHT CHANDELIER

P4700-20 Antique Bronze
Size: 24" dia., 14-1/4" ht.
Overall ht. w/stem 80"; wire 15'.
Lamps: Five medium base lamps, each 100w max.

MINI-PENDANT

P5082-20 Antique Bronze
Size: 6" dia., 9-3/4" ht.
Overall ht. w/stem 76"; wire 10'.
Lamp: One medium base lamp, 100w max.

ONE-LIGHT WALL SCONCE

P7149-20 Antique Bronze
Size: 8" W., 8" ht.
Extends 4". H/CTR 4".
Lamp: One medium base lamp, 75w max.
ADA



P7149-20



P5082-20



P4700-20

Indi



Shown: P4248-134 chandelier

MINI-PENDANT

P5074-20 Antique Bronze

P5074-134 Silver Ridge

Size: 9-1/2" dia., 11" ht.

Overall ht. w/stem 77"; wire 10'.

Lamp: One medium base lamp,
100w max.



P5074-20



P5074-134

All stem-hung fixtures shown on this spread include one 6" stem, four 12" stems and 6 links of chain.

SLIGHTLY LARGER IN SCALE THAN A TRADITIONAL PENDANT, INDI FIXTURES ARE ARTISTICALLY STYLED AND CAN BE CLUSTERED TO FILL SPACIOUS INTERIOR AREAS. ANTIQUE MIRRORED GLASS SHINES THROUGH WHEN ILLUMINATED.



P4248-20



P4248-134

THREE-LIGHT CHANDELIER
P4248-20 Antique Bronze
P4248-134 Silver Ridge
Size: 18" dia., 19-1/2" ht.
Overall ht. w/stem 86"; wire 15'.
Lamps: Three medium base lamps, each 100w max.

Prosper



THREE-LIGHT INVERTED PENDANT

P3700-20 Antique Bronze
Size: 17-3/8" dia., 23-1/2" ht.
Overall ht. w/stem 89-1/2"; wire 15'.
Lamps: Three medium base lamps,
each 100w max.



SKG0905LED27 or P7818-01
lamp recommended.



*Shown: P4702-20 chandelier with
P2151-20 wall bracket.*

A FRAME INSPIRED BY MODERN GRAPHIC DESIGN
THRIVES IN THIS COLLECTION BY PROVIDING ARTFUL
DETAILS TO ENHANCE VISUAL SPACE.

EXQUISITE HANDMADE, POLISHED SEEDED GLASS IS
ETCHED INSIDE FOR PLEASING ILLUMINATION.

SEMI-FLUSH CONVERTIBLE

P3422-20 Antique Bronze
Size: 13-3/8" dia., 11-3/4" ht.
Overall ht. w/stem 78-1/2";
wire 15'.
Lamps: Two medium base
lamps, each 100w max.

FIVE-LIGHT CHANDELIER

P4702-20 Antique Bronze
Size: 30" dia., 24-1/2" ht. Overall
ht. w/stem 90-1/2"; wire 15'.
Lamps: Five G9 halogen lamps,
each 60w max.

MINI-PENDANT

P5086-20 Antique Bronze
Size: 9" dia., 7" ht. Overall ht.
w/stem 73"; wire 10'.
Lamp: One G9 halogen lamp,
60w max.



*All Prosper hanging fixtures
include one 6" stem, four 12"
stems and 6 links of chain.*

Prosper



THREE-LIGHT CHANDELIER

P4701-20 Antique Bronze
Size: 25" dia., 20-1/2" ht. Overall
ht. w/stem 86"; wire 15'.
Lamps: Three G9 halogen lamps,
each 60w max.

NINE-LIGHT CHANDELIER

P4703-20 Antique Bronze
Two-tier.
Size: 34-1/2" dia., 27-7/8" ht.
Overall ht. w/stem 94"; wire 15'.
Lamps: Nine G9 halogen lamps,
each 60w max.

A FRAME INSPIRED BY MODERN GRAPHIC DESIGN
THRIVES IN THIS COLLECTION BY PROVIDING ARTFUL
DETAILS TO ENHANCE VISUAL SPACE.

ONE-LIGHT BATH

P2150-20 Antique Bronze
Size: 9" W., 14-1/4" ht.
Extends 10-1/4". H/CTR 4-1/2".
Lamp: One G9 halogen lamp,
60w max.

TWO-LIGHT BATH


P2151-20 Antique Bronze
Size: 19-5/8" W., 7-1/2" ht.
Extends 10". H/CTR 4-3/8".
Lamps: Two G9 halogen lamps,
each 60w max.

THREE-LIGHT BATH

P2152-20 Antique Bronze
Size: 30-1/8" W., 7-3/8" ht.
Extends 10". H/CTR 4-3/8".
Lamps: Three G9 halogen
lamps, each 60w max.

FOUR-LIGHT BATH

P2153-20 Antique Bronze
Size: 40-5/8" W., 7-3/8" ht.
Extends 10". H/CTR 4-3/8".
Lamps: Four G9 halogen
lamps, each 60w max.



SKG0905LED27 or P7818-01
lamp recommended.

Bath fixtures mount up or down.

Ridge

P4657-84



P4698-84



FOUR-LIGHT CHANDELIER

P4657-84 Espresso
 Size: 16" dia., 19-3/4" ht. Overall
 ht. w/chain 94"; wire 15'.
 Lamps: Four medium base
 lamps, each 100w max.

FOUR-LIGHT LINEAR CHANDELIER

P4698-84 Espresso
 Includes two sets of stems.
 Size: 36" L., 4" W., 11" ht. Overall
 ht. w/stem 77"; wire 15'.
 Lamps: Four medium base lamps,
 each 100w max.

MINI-PENDANT

P5009-84 Espresso
 Size: 6-1/4" dia., 10-3/4" ht.
 Overall ht. w/stem 77"; wire 10'.
 Lamp: One medium base lamp,
 100w max.

WALL BRACKET

P7143-84 Espresso
 Mounts up or down.
 Size: 6-1/4" W., 10-3/4" ht.
 Extends 5-3/8". H/CTR 5-3/8".
 Lamp: One medium base lamp,
 100w max.

P5009-84



P7143-84

*All Ridge stem-hung fixtures
 include one 6" stem, four 12"
 stems and 6 links of chain.*

A CLASSICALLY DESIGNED FIXTURE FAMILY FOR URBAN CHIC ENVIRONMENTS, RIDGE FEATURES A CLEAN, YET RUSTIC, MODERN FRAME. THE OPEN DESIGN ENCASES AN ETCHED ANTIQUE WATERMARK GLASS SHADE WITH A TAPERED SQUARE FORM.



P3571-84



P4658-84

FOUR-LIGHT FOYER
P3571-84 Espresso
Size: 20-1/2" dia., 34-3/8" ht.
Overall ht. w/chain 108-1/2";
wire 15'.
Lamps: Four medium base
lamps, each 100w max.
FIVE-LIGHT CHANDELIER
P4658-84 Espresso
Size: 22" dia., 23-3/8" ht. Overall
ht. w/chain 98"; wire 15'.
Lamps: Five medium base
lamps, each 100w max.

Enclave

THREE-LIGHT CONVERTIBLE

P3671-71 Gilded Iron
Size: 15" dia., 13-1/4" ht.
Overall ht. w/chain 54"; wire 10'.
Lamps: Three medium base lamps, each 100w max.

THREE-LIGHT FOYER

P3691-71 Gilded Iron
Size: 16" dia., 26" ht.
Overall ht. w/chain 101"; wire 15'.
Lamps: Three candelabra base lamps, each 60w max.

NINE-LIGHT FOYER

P3692-71 Gilded Iron
Two-tier.
Size: 24" dia., 38" ht. Overall ht. w/chain 113"; wire 15'.
Lamps: Nine candelabra base lamps, each 60w max.

P3671-71




P3671-71



P3692-71



P3691-71



Shown: Bottom of chandelier.

AN AUTHENTIC WROUGHT IRON FRAME AND CLASSIC SCROLLWORK ACCENTS EMBRACE THIS FAMILY. FINISHED WITH RICH, TEXTURED GLASS SHADES, THESE PIECES ARE IDEAL IN LARGER HOMES FEATURING UPSCALE STYLE PREFERENCES.



P7165-71

ONE-LIGHT WALL SCONCE

P7165-71 Gilded Iron
Size: 6" W., 16-1/2" ht.
Extends 7". H/CTR 7".
Lamp: One medium base lamp, 100w max.

NINE-LIGHT CHANDELIER

P4731-71 Gilded Iron
Two-tier.
Size: 35" dia., 42" ht. Overall ht. w/chain 164"; wire 15'.
Lamps: Nine medium base lamps, each 100w max.



AN AUTHENTIC WROUGHT IRON FRAME AND CLASSIC SCROLLWORK ACCENTS EMBRACE THIS FAMILY. FINISHED WITH RICH, TEXTURED GLASS SHADES, THESE PIECES ARE IDEAL IN LARGER HOMES FEATURING UPSCALE STYLE PREFERENCES.

Enclave

THREE-LIGHT CHANDELIER

P4729-71 Gilded Iron
Size: 24" dia., 22-3/8" ht.
Overall ht. w/chain 97"; wire 15'.
Lamps: Three medium base lamps, each 100w max.

SIX-LIGHT CHANDELIER

P4730-71 Gilded Iron
Size: 28" dia., 26-3/8" ht.
Overall ht. w/chain 101"; wire 15'.
Lamps: Three medium base lamps, each 100w max.

MINI-PENDANT

P5071-71 Gilded Iron
Includes one 6", four 12" stems.
and 6 links of chain.
Size: 6" dia., 16-1/2" ht.
Overall ht. w/stem 82"; wire 10'.
Lamp: One medium base lamp, 100w max.



Monogram

AN EXAMPLE OF GENUINE CRAFTSMANSHIP, MONOGRAM MAKES ITS MARK WITH MODERN, YET SIMPLE, SCROLLING FORMS. A WATERMARK FINISH CREATES RICH DEPTH ON THE GLASS DIFFUSERS SUPPORTED BY THE ELEGANT BRONZE FINISH FRAME.



P4738-102

NINE-LIGHT CHANDELIER

P4738-102 Roasted Java

Two-tier.

Size: 36" dia., 44" ht. Overall ht. w/chain 167"; wire 15'.

Lamps: Nine medium base lamps, each 100w max.

ONE-LIGHT WALL SCONCE

P7167-102 Roasted Java

Size: 6-7/8" W., 15-7/8" ht.

Extends 9-5/8". H/CTR 7-7/8".

Lamp: One medium base lamp, 100w max.



P7167-102

Monogram



TWO-LIGHT CONVERTIBLE

P3674-102 Roasted Java
Size: 17" dia., 14-7/8" ht.
Overall ht. w/chain 55"; wire 10'.
Lamps: Two medium base lamps, each 100w max.

THREE-LIGHT INVERTED PENDANT

P3689-102 Roasted Java
Size: 22-1/4" dia., 33" ht.
Overall ht. w/chain 108"; wire 15'.
Lamps: Three medium base lamps, each 100w max.



MINI-PENDANT

P5621-102 Roasted Java
Includes one 6", four 12" stems.
and 6 links of chain.
Size: 6-7/8" dia., 11-1/4" ht.
Overall ht. w/stem 77"; wire 10'.
Lamp: One medium base lamp, 100w max.

AN EXAMPLE OF GENUINE CRAFTSMANSHIP, MONOGRAM MAKES ITS MARK WITH MODERN, YET SIMPLE, SCROLLING FORMS. A WATERMARK FINISH CREATES RICH DEPTH ON THE GLASS DIFFUSERS SUPPORTED BY THE ELEGANT BRONZE FINISH FRAME.



THREE-LIGHT CHANDELIER

P4736-102 Roasted Java
Size: 24" dia., 21" ht.
Overall ht. w/chain 96"; wire 15'.
Lamps: Three medium base lamps, each 100w max.

SIX-LIGHT CHANDELIER

P4737-102 Roasted Java
Size: 28" dia., 33-3/4" ht.
Overall ht. w/chain 109"; wire 15'.
Lamps: Six medium base lamps, each 100w max.

Lucky



THREE-LIGHT CONVERTIBLE

P3664-09 Brushed Nickel
P3664-15 Polished Chrome
Includes one 12" stem and 6 links of chain.
Size: 16-1/4" dia., 13-1/4" ht.
Overall ht. w/stem 79"; wire 10'.
Lamps: Three medium base lamps, each 100w max.

THREE-LIGHT CHANDELIER

P4721-09 Brushed Nickel
P4721-15 Polished Chrome
Size: 22" dia., 16" ht.
Overall ht. w/stem 82"; wire 15'.
Lamps: Three medium base lamps, each 100w max.

MINI-PENDANT

P5088-09 Brushed Nickel
P5088-15 Polished Chrome
Size: 5" dia., 7-1/4" ht.
Overall ht. w/stem 73"; wire 10'.
Lamp: One medium base lamp, 100w max.



LIGHT IS BEAUTIFULLY ILLUMINATED THROUGH SOFT PRISMATIC GLASS IN THE LUCKY COLLECTION. PRECISE DETAILS IN THE TUBING, FRAME AND SHADES ENHANCE THE VINTAGE DESIGN STYLING.



FIVE-LIGHT CHANDELIER

P4722-09 Brushed Nickel
P4722-15 Polished Chrome
Size: 25" dia., 18" ht.
Overall ht. w/stem 82"; wire 15'.
Lamps: Five medium base lamps, each 100w max.

ONE-LIGHT PENDANT

P5119-09 Brushed Nickel
P5119-15 Polished Chrome
Size: 16-1/4" dia., 14-3/4" ht.
Overall ht. w/stem 81"; wire 10'.
Lamp: One medium base lamp, 100w max.



All stem-hung fixtures on this page includes one 6", four 12" stems, and 6 links of chain except where noted.

LIGHT IS BEAUTIFULLY ILLUMINATED THROUGH SOFT PRISMATIC GLASS IN THE LUCKY COLLECTION. PRECISE DETAILS IN THE TUBING, FRAME AND SHADES ENHANCE THE VINTAGE DESIGN STYLING.

Lucky



SEVEN-LIGHT CHANDELIER

P4724-09 Brushed Nickel

P4724-15 Polished Chrome

Size: 31" dia., 22-1/2" ht.

Overall ht. w/stem 88"; wire 15'.

Lamps: Seven medium base lamps, each 100w max.





P3667-09



P3667-15



P4723-09



P4723-15

THREE-LIGHT FLUSH MOUNT

P3667-09 Brushed Nickel

P3667-15 Polished Chrome

Size: 15" dia., 7" ht.

Lamps: Three medium base lamps, each 60w max.

FIVE-LIGHT CHANDELIER

P4723-09 Brushed Nickel

P4723-15 Polished Chrome

Size: 25" dia., 17" ht.

Overall ht. w/stem 83"; wire 15".

Lamps: Five medium base lamps, each 100w max.

Shown: P5119-09 pendant.

All stem-hung fixtures on this page includes one 6", four 12" stems, and 6 links of chain.

SMOOTH FORMS AND WINDOWPANE STYLE GALLERY PRODUCE A BEAUTIFUL, MODERN GAS LIGHT EFFECT. OVERSCALE TUBING AND GLASS SHADES OFFER SUBSTANCE WITHIN THE SLEEK FRAME.

Cascadia

TWO-LIGHT CONVERTIBLE

P3644-15 Polished Chrome

P3644-20 Antique Bronze

Size: 14" dia., 10" ht.

Overall ht. w/chain 49"; wire 10'.

Lamps: Two medium base lamps, each 100w max.

FIVE-LIGHT CHANDELIER

P4613-15 Polished Chrome

P4613-20 Antique Bronze

Size: 26" dia., 10-3/4" ht.

Overall ht. w/stem 83"; wire 15'.

Lamps: Five medium base lamps, each 100w max.





TWO-LIGHT FLUSH MOUNT

P3633-15 Polished Chrome
P3633-20 Antique Bronze
 Size: 14" dia., 6" ht.
 Lamps: Two medium base lamps, each 60w max.

THREE-LIGHT CHANDELIER

P4612-15 Polished Chrome
P4612-20 Antique Bronze
 Size: 21" dia., 16-3/4" ht.
 Overall ht. w/stem 83"; wire 15'.
 Lamps: Three medium base lamps, each 100w max.

MINI-PENDANT

P5066-15 Polished Chrome
P5066-20 Antique Bronze
 Size: 5-7/8" dia., 6-3/4" ht.
 Overall ht. w/stem 73"; wire 10'.
 Lamp: One medium base lamp, 100w max.



All stem-hung fixtures on this page include one 6", four 12" stems, and 6 links of chain.

SMOOTH FORMS AND WINDOWPANE STYLE GALLERY PRODUCE A BEAUTIFUL, MODERN GAS LIGHT EFFECT. OVERSCALE TUBING AND GLASS SHADES OFFER SUBSTANCE WITHIN THE SLEEK FRAME.

Cascadia

NINE-LIGHT CHANDELIER

P4614-15 Polished Chrome

P4614-20 Antique Bronze

Two-tier

Size: 30" dia., 21-7/8" ht.

Overall ht. w/chain 88"; wire 15'

Lamps: Nine medium base lamps, each 100w max.



All stem-hung fixtures on this page include one 6", four 12" stems, and 6 links of chain.

ONE-LIGHT BATH

P2146-15 Polished Chrome
P2146-20 Antique Bronze
Size: 5-7/8" W., 8" ht.
Extends 6-1/2". H/CTR 5-1/2".
Lamp: One medium base lamp, 100w max.

TWO-LIGHT BATH

P2147-15 Polished Chrome
P2147-20 Antique Bronze
Size: 16" W., 8" ht.
Extends 6-1/2". H/CTR 5-5/8".
Lamps: Two medium base lamps, each 100w max.

THREE-LIGHT BATH

P2148-15 Polished Chrome
P2148-20 Antique Bronze
Size: 24-1/8" W., 8" ht.
Extends 6-1/2". H/CTR 5-5/8".
Lamps: Three medium base lamps, each 100w max.

FOUR-LIGHT BATH

P2149-15 Polished Chrome
P2149-20 Antique Bronze
Size: 32" W., 8" ht.
Extends 6-1/2". H/CTR 5-5/8".
Lamps: Four medium base lamps, each 100w max.



P2147-20



P2147-15



P2148-20



P2148-15



P2149-15



P2146-15



P2146-20



P2149-20

All bath fixtures mount up or down.

CHERISH

FIVE-LIGHT LINEAR CHANDELIER



P4617-09 Brushed Nickel

P4617-20 Antique Bronze

Size: 40" L., 12" W., 20-3/8" ht.

Overall ht. w/chain 95"; wire 15'.

Lamps: Five candelabra base lamps, each 60w max.



Coordinates with Markor and Arden fixtures.

TRADITIONAL LINEAR ISLAND LIGHT AND ELEGANT CHANDELIER OPTIONS ARE MODERNIZED WITH A SUMMER LINEN SHADE. THE ANTIQUE BRONZE FIXTURES INCLUDE BOTH BRONZE AND NATURAL BRASS CANDLE COVER OPTIONS ALLOWING HOMEOWNERS TO COMPLEMENT MIXED METAL STYLING WITHIN A ROOM.



P7172-09



P7172-20
Shown with natural brass
candle covers



P7172-20
Shown with antique bronze
candle covers



P4618-20



P4618-09

SIX-LIGHT CHANDELIER

P4618-09 Brushed Nickel

P4618-20 Antique Bronze

Size: 24" dia., 22-3/8" ht.

Overall ht. w/chain 97"; wire 15'.

Lamps: Six candelabra base
lamps, each 60w max.

TWO-LIGHT WALL SCONCE

P7172-09 Brushed Nickel

P7172-20 Antique Bronze

Size: 12" W., 9" ht.

Extends 6-1/2". H/CTR 4-3/4".

Lamps: Two candelabra base
lamps, each 60w max.

Arden



FIVE-LIGHT CHANDELIER
P4746-09 Brushed Nickel
P4746-20 Antique Bronze
Size: 24-5/8" dia., 22-1/4" ht.
Overall ht. w/chain 97"; wire 15'.
Lamps: Five medium base
lamps, each 100w max.

Shown: P3905-09 pendant

ARDEN OFFERS A COMFORTABLE SILHOUETTE THAT IS BOTH RUSTIC AND MODERN. A SUBSTANTIAL FRAME IS CRAFTED FROM OVERSCALE TUBING TO HEIGHTEN THE EFFECT. FIXTURES FEATURE EITHER ETCHED GLASS OR A SUMMER LINEN FABRIC SHADE THAT COORDINATE WELL WITH OTHER PROGRESS LIGHTING STYLES, SUCH AS CHERISH.

TWO-LIGHT SEMI-FLUSH CONVERTIBLE

P3720-09 Brushed Nickel
P3720-20 Antique Bronze
 Size: 14" dia., 11-3/8" ht. Overall ht. w/chain 50"; wire 10'.
 Lamps: Two medium base lamps, each 100w max.



P3720-09



P3720-20

TWO-LIGHT FLUSH MOUNT

P3739-09 Brushed Nickel
P3739-20 Antique Bronze
 Size: 14" dia., 6-5/8" ht.
 Lamps: Two medium base lamps, each 60w max.



P3739-20



P3739-09

THREE-LIGHT CHANDELIER

P4745-09 Brushed Nickel
P4745-20 Antique Bronze
 Size: 22" dia., 18-3/4" ht. Overall ht. w/chain 93"; wire 15'.
 Lamps: Three medium base lamps, each 100w max.



P4745-20

NINE-LIGHT CHANDELIER

P4747-09 Brushed Nickel
P4747-20 Antique Bronze
 Two-tier
 Size: 30-1/2" dia., 30" ht. Overall ht. w/chain 153"; wire 15'.
 Lamps: Nine medium base lamps, each 100w max.



P4747-09



P4745-09



Arden

THREE-LIGHT INVERTED PENDANT

P3905-09 Brushed Nickel
P3905-20 Antique Bronze
Size: 18-1/8" dia., 24-5/8" ht.
Overall ht. w/stem 99"; wire 10 ft.
Lamps: Three medium base lamps, each 100w max.

TWELVE-LIGHT CHANDELIER

P4748-09 Brushed Nickel
P4748-20 Antique Bronze
Three-tier.
Size: 42" dia., 41-1/2" ht.
Overall ht. w/chain 164"; wire 15'.
Lamps: Twelve medium base lamps, each 75w max.

MINI-PENDANT

P5092-20 Antique Bronze
P5092-104 Polished Nickel
Includes one 6", four 12" stems, and 6 links of chain.
Size: 5-7/8" dia., 9-5/8" ht.
Overall ht. w/chain 75-1/2"; wire 10'.
Lamp: One medium base lamp, 100w max.

P4748-20



P3905-09



P3905-20



P5092-20



P5092-09



ARDEN OFFERS A COMFORTABLE SILHOUETTE THAT IS BOTH RUSTIC AND MODERN. A SUBSTANTIAL FRAME IS CRAFTED FROM OVERSCALE TUBING TO HEIGHTEN THE EFFECT. FIXTURES FEATURE EITHER ETCHED GLASS OR A SUMMER LINEN FABRIC SHADE THAT COORDINATE WELL WITH OTHER PROGRESS LIGHTING STYLES, SUCH AS CHERISH.

ONE-LIGHT BATH

P2127-09 Brushed Nickel
P2127-20 Antique Bronze
 Size: 5-7/8" W., 8" ht.
 Extends 8-1/4". H/CTR 4".
 Lamp: One medium base lamp, 100w max.

FOUR-LIGHT BATH

P2130-09 Brushed Nickel
P2130-20 Antique Bronze
 Size: 34" W., 7-1/2" ht.
 Extends 8-1/4". H/CTR 4-5/8".
 Lamps: Four medium base lamps, each 100w max.

TWO-LIGHT BATH

P2128-09 Brushed Nickel
P2128-20 Antique Bronze
 Size: 16-1/2" W., 7-1/2" ht.
 Extends 8-1/8". H/CTR 4-5/8".
 Lamps: Two medium base lamps, each 100w max.

THREE-LIGHT BATH

P2129-09 Brushed Nickel
P2129-20 Antique Bronze
 Size: 24-1/2" W., 7-1/2" ht.
 Extends 8-1/4". H/CTR 4-5/8".
 Lamps: Three medium base lamps, each 100w max.



P2127-09



P2127-20



P2128-20



P2129-09



P2129-20



P2128-09



P2130-09



P2130-20

All bath fixtures mount up or down.

Keats



P3887-20

THREE-LIGHT FOYER

P3887-09 Brushed Nickel
P3887-20 Antique Bronze
Size: 15" dia., 25-3/4" ht.
Overall ht. w/chain 100-1/2";
wire 15'.
Lamps: Three medium base
lamps, each 100w max.



Shown: P3891-20 chandelier

KEATS CONTRIBUTES TO A LIGHT AND OPEN ATMOSPHERE FOR TRADITIONAL STYLING. FROSTED RIBBED GLASS AND AN ELEGANT FRAME ENHANCE THE OVERALL EFFECT.



THREE-LIGHT CHANDELIER

P4749-09 Brushed Nickel
P4749-20 Antique Bronze
Size: 19-5/8" dia., 19-3/8" ht.
Overall ht. w/chain 95";
wire 15'.
Lamps: Three medium base
lamps, each 100w max.



KEATS CONTRIBUTES TO A LIGHT AND OPEN ATMOSPHERE FOR TRADITIONAL STYLING. FROSTED RIBBED GLASS AND AN ELEGANT FRAME ENHANCE THE OVERALL EFFECT.

Keats

TWELVE-LIGHT CHANDELIER

P4752-09 Brushed Nickel

P4752-20 Antique Bronze

Three-tier.

Size: 44-1/2" dia., 45-1/4" ht.

Overall ht. w/chain 168"; wire 15'.

Lamps: Twelve medium base lamps, each 75w max.

P4752-09





FOUR-LIGHT FOYER

P3891-09 Brushed Nickel

P3891-20 Antique Bronze

Size: 21" dia., 32-3/4" ht.

Overall ht. w/chain 107"; wire 15'.

Lamps: Four medium base lamps, each 100w max.

FIVE-LIGHT CHANDELIER

P4750-09 Brushed Nickel

P4750-20 Antique Bronze

Size: 24-1/2" dia., 22-1/8" ht.

Overall ht. w/chain 97"; wire 15'.

Lamps: Five medium base lamps, each 100w max.



Keats

ONE-LIGHT BATH

P2814-09 Brushed Nickel

P2814-20 Antique Bronze

Size: 5-3/4" W., 9" ht.

Extends 8-1/8". H/CTR 5-1/4".

Lamp: One medium base lamp, 100w max.

NINE-LIGHT CHANDELIER

P4751-09 Brushed Nickel

P4751-20 Antique Bronze

Two-tier.

Size: 30-1/2" dia., 32-3/4" ht.

Overall ht. w/chain 107"; wire 15'.

Lamps: Nine medium base lamps, each 100w max.

MINI-PENDANT

P5093-09 Brushed Nickel

P5093-20 Antique Bronze

Includes one 6", four 12" stems, and 6 links of chain.

Size: 5-3/4" dia., 6-3/4" ht.

Overall ht. w/stem 73"; wire 10'.

Lamp: One medium base lamp, 100w max.



KEATS CONTRIBUTES TO A LIGHT AND OPEN ATMOSPHERE FOR TRADITIONAL STYLING. FROSTED RIBBED GLASS AND AN ELEGANT FRAME ENHANCE THE OVERALL EFFECT.

TWO-LIGHT BATH

P2820-09 Brushed Nickel
P2820-20 Antique Bronze
 Size: 15-1/2" W., 8-5/8" ht.
 Extends 8-1/8". H/CTR 5-1/4".
 Lamps: Two medium base lamps, each 100w max.

THREE-LIGHT BATH

P2821-09 Brushed Nickel
P2821-20 Antique Bronze
 Size: 24-3/8" W., 8-3/4" ht.
 Extends 9-1/2". H/CTR 5-1/4".
 Lamps: Three medium base lamps, each 100w max.

FOUR-LIGHT BATH

P2822-09 Brushed Nickel
P2822-20 Antique Bronze
 Size: 29-3/8" W., 8-3/4" ht.
 Extends 9-1/2". H/CTR 5-1/4".
 Lamps: Four medium base lamps, each 100w max.



P2822-09



P2821-20



P2821-09



P2820-20



P2820-09



P2822-20

All bath fixtures mount up or down.

progresslighting.com

Sally



P3795-09

FIVE-LIGHT CHANDELIER

P4741-09 Brushed Nickel

P4741-20 Antique Bronze

Size: 25" dia., 19" ht.

Overall ht. w/chain 95"; wire 15'.

Lamps: Five medium base lamps, each 100w max.



P4741-20



Shown: P3787-20 foyer

TALLY EMBRACES A SIMPLIFIED CLASSIC FORM THAT IS UPDATED WITH MODERN INSPIRATION. ANGULAR ARMS AND LINEN-FINISHED GLASS OFFER VISUAL INTEREST AND ENHANCE RELAXED ENVIRONMENTS.

FOUR-LIGHT FOYER

P3786-09 Brushed Nickel
P3786-20 Antique Bronze
 Size: 11-7/8" dia., 19-1/4" ht.
 Overall ht. w/chain 94"; wire 15'.
 Lamps: Four candelabra base lamps, each 60w max.

FOUR-LIGHT FOYER

P3787-09 Brushed Nickel
P3787-20 Antique Bronze
 Size: 16-3/4" dia., 26-1/2" ht.
 Overall ht. w/chain 101"; wire 15'.
 Lamps: Four candelabra base lamps, each 60w max.

EIGHT-LIGHT FOYER

P3795-09 Brushed Nickel
P3795-20 Antique Bronze
 Two-tier.
 Size: 20-1/4" dia., 32-7/8" ht.
 Overall ht. w/chain 108"; wire 15'.
 Lamps: Eight candelabra base lamps, each 60w max.



Tally

TALLY EMBRACES A SIMPLIFIED CLASSIC FORM THAT IS UPDATED WITH MODERN INSPIRATION. ANGULAR ARMS AND LINEN-FINISHED GLASS OFFER VISUAL INTEREST AND ENHANCE RELAXED ENVIRONMENTS.



P4740-09



P4740-20



P4743-09



P4743-20

THREE-LIGHT CHANDELIER

P4740-09 Brushed Nickel
P4740-20 Antique Bronze
Size: 22" dia., 17-1/2" ht.
Overall ht. w/chain 93"; wire 15'.
Lamps: Three medium base lamps, each 100w max.

NINE-LIGHT CHANDELIER

P4743-09 Brushed Nickel
P4743-20 Antique Bronze
Two-tier.
Size: 30" dia., 30" ht.
Overall ht. w/chain 154"; wire 15'.
Lamps: Nine medium base lamps, each 100w max.



P5664-09



P5664-20

MINI-PENDANT

P5664-09 Brushed Nickel
P5664-20 Antique Bronze
Includes one 6", four 12" stems. and 6 links of chain.
Size: 6-1/4" dia., 7-1/4" ht.
Overall ht. w/stem 73-1/2"; wire 10'.
Lamp: One medium base lamp, 100w max.




P2761-09



P2761-15



P2761-20



P2762-20



P2762-09



P2764-20

ONE-LIGHT BATH

P2761-09 Brushed Nickel
P2761-15 Polished Chrome
P2761-20 Antique Bronze
Size: 6-1/4" W., 10" ht.
Extends 9-3/8". H/CTR 5".
Lamp: One medium base lamp, 100w max.

FOUR-LIGHT BATH

P2764-09 Brushed Nickel
P2764-15 Polished Chrome
P2764-20 Antique Bronze
Size: 28-7/8" W., 10" ht.
Extends 9-1/4". H/CTR 5".
Lamps: Four medium base lamps, each 100w max..



P2764-15

TWO-LIGHT BATH

P2762-09 Brushed Nickel
P2762-15 Polished Chrome
P2762-20 Antique Bronze
Size: 13-3/4" W., 10" ht.
Extends 9-1/4". H/CTR 5".
Lamps: Two medium base lamps, each 100w max.



P2763-15

THREE-LIGHT BATH

P2763-09 Brushed Nickel
P2763-15 Polished Chrome
P2763-20 Antique Bronze
Size: 22-3/4" W., 10" ht.
Extends 9". H/CTR 5".
Lamps: Three medium base lamps, each 100w max.



P2763-09

All bath fixtures mount up or down.

Aleya



THREE-LIGHT FOYER

P3846-20 Antique Bronze
Size: 18" dia., 24-3/8" ht.
Overall ht. w/chain 99"; wire 15'.
Lamps: Three medium base
lamps, each 100w max.



*Shown: P4459-20 chandelier and
P2959-20 sconce.*

TRADITIONAL AND MODERN STYLES COME TOGETHER IN THE ALEXA COLLECTION. FEATURING A NEW -20 ANTIQUE BRONZE FINISH, THE ALEXA FAMILY OFFERS A FRESH TWIST TO CONTEMPORARY INDUSTRIAL STYLING.

ETCHED UMBER LINEN FINISHED GLASS – COMPLEMENTED WITH A CRISP, CLEAR EDGE ACCENT STRIP - ADDS A WARM FEEL TO THIS MODERN FIXTURE FAMILY.

FOUR-LIGHT FOYER

P3977-20 Antique Bronze
Size: 18" W., 44-3/8" ht. Overall ht. w/chain 119"; wire 15'.
Lamps: Four medium base lamps, each 100w max.

THREE-LIGHT CHANDELIER

P4458-20 Antique Bronze
Size: 17" dia., 19-5/8" ht. Overall ht. w/chain 95"; wire 15'.
Lamps: Three medium base lamps, each 100w max.

FIVE-LIGHT CHANDELIER

P4459-20 Antique Bronze
Size: 20" dia., 19-7/8" ht. Overall ht. w/chain 95"; wire 15'.
Lamps: Five medium base lamps, each 100w max.

MINI-PENDANT

P5147-20 Antique Bronze
Includes two 6", one 12" and two 15" stems with 90° swivel.
Size: 4" dia., 7-5/8" ht. Overall ht. w/stem 64"; wire 10'.
Lamp: One medium base lamp, 100w max.



Alexa



P4626-20



P4619-20

NINE-LIGHT CHANDELIER
P4626-20 Antique Bronze
Two-tier.
Size: 28" dia., 28-1/2" ht. Overall
ht. w/chain 102"; wire 15'.
Lamps: Nine medium base
lamps, each 60w max.

**FOUR-LIGHT LINEAR
CHANDELIER**
P4619-20 Antique Bronze
Size: 34" L., 4-1/2" W., 20" ht.
Overall ht. w/chain 93"; wire 15'.
Lamps: Four medium base
lamps, each 60w max.

TRADITIONAL AND MODERN STYLES COME TOGETHER IN THE ALEXA COLLECTION. FEATURING A NEW -20 ANTIQUE BRONZE FINISH, THE ALEXA FAMILY OFFERS A FRESH TWIST TO CONTEMPORARY INDUSTRIAL STYLING.

ETCHED UMBER LINEN FINISHED GLASS – COMPLEMENTED WITH A CRISP, CLEAR EDGE ACCENT STRIP - ADDS A WARM FEEL TO THIS MODERN FIXTURE FAMILY.

TWO-LIGHT SEMI-FLUSH

P2851-20 Antique Bronze
Size: 12-1/4" dia., 11" ht.
Lamps: Two medium base lamps, each 100w max.

ONE-LIGHT BATH

P2959-20 Antique Bronze
Size: 4-1/2" W., 9-3/8" ht.
Extends 6-1/8". H/CTR 5-7/8".
Lamp: One medium base lamp, 100w max.

TWO-LIGHT BATH

P2977-20 Antique Bronze
Size: 13" W., 9-1/2" ht.
Extends 6-1/8". H/CTR 7-1/4".
Lamps: Two medium base lamps, each 100w max.

THREE-LIGHT BATH

P2978-20 Antique Bronze
Size: 22" W., 9-1/2" ht.
Extends 6-1/8". H/CTR 7-1/4".
Lamps: Three medium base lamps, each 100w max.

FOUR-LIGHT BATH

P2998-20 Antique Bronze
Size: 31" W., 9-1/2" ht.
Extends 6-1/8". H/CTR 7-1/4".
Lamps: Four medium base lamps, each 100w max.



P2977-20



P2978-20



P2851-20



P2959-20



P2998-20

Applause



SEMI-FLUSH CONVERTIBLE

P3507-09 Brushed Nickel
 Size: 15-3/4" dia., 12" ht.
 Overall ht. w/chain 51"; wire 10'.
 Lamps: Two medium base lamps, each 100w max.

INVERTED PENDANT

P3560-09 Brushed Nickel
 Size: 19-5/8" dia., 21-3/8" ht.
 Overall ht. w/stem 96-1/2"; wire 15'.
 Lamps: Three medium base lamps, each 100w max.



THREE-LIGHT CHANDELIER

P4035-09 Brushed Nickel
 Size: 20" dia., 15-3/4" ht. Overall ht. w/chain 91"; wire 15'.
 Lamps: Three medium base lamps, each 100w max.

INDIVIDUALS DEMONSTRATE APPRECIATION AND PRAISE FOR ELEMENTS THAT ARE WORTHY OF ACCLAIM. A COLLECTION DESERVING OF RECOGNITION, APPLAUSE IS COMPRISED OF ETCHED PARCHMENT GLASS PAIRED WITH A CLASSIC IRON FORM.



FIVE-LIGHT CHANDELIER

P4036-09 Brushed Nickel
Size: 24-1/2" dia., 24-5/8" ht.
Overall ht. w/chain 99"; wire 15'.
Lamps: Five medium base lamps, each 100w max.

NINE-LIGHT CHANDELIER

P4037-09 Brushed Nickel
Two-tier.
Size: 29-1/4" dia., 31-3/4" ht. Overall ht. w/chain 145-1/2"; wire 15'.
Lamps: Nine medium base lamps, each 100w max.

MINI-PENDANT

P5010-09 Brushed Nickel
Includes one 6" stem, four 12" stems and 6 links of chain.
Size: 7" dia., 6-1/2" ht.
Overall ht. w/stem 72-1/2"; wire 10'.
Lamp: One medium base lamp, 100w max.



Applause

TWO-LIGHT LINEAR CHANDELIER

P4321-09 Brushed Nickel

P4321-20 Antique Bronze

Size: 36" L., 14" W., 18-1/4" ht.

Overall ht. w/chain 93"; wire 15'.

Lamps: Two medium base lamps, each 100w max.

TWELVE-LIGHT CHANDELIER

P4654-09 Brushed Nickel

P4654-20 Antique Bronze

Three-tier.

Size: 42" dia., 38" ht. Overall ht. w/ chain 161"; wire 15'.

Lamps: Twelve medium base lamps, each 75w max.



P4321-09



P4321-20



INDIVIDUALS DEMONSTRATE APPRECIATION AND PRAISE FOR ELEMENTS THAT ARE WORTHY OF ACCLAIM. A COLLECTION DESERVING OF RECOGNITION, APPLAUSE IS COMPRISED OF ETCHED PARCHMENT GLASS PAIRED WITH A CLASSIC IRON FORM.

ONE-LIGHT BATH

P2095-09 Brushed Nickel
 Size: 7" W., 9-1/8" ht.
 Extends 7-7/8". H/CTR 5-3/4".
 Lamp: One medium base lamp, 100w max.



P3617-09



P2095-09

TWO-LIGHT BATH

P2096-09 Brushed Nickel
 Size: 16-1/4" W., 8-1/2" ht.
 Extends 9". H/CTR 6".
 Lamps: Two medium base lamps, each 100w max.



P3617-20

THREE-LIGHT BATH

P2097-09 Brushed Nickel
 Size: 24" W., 8-1/2" ht.
 Extends 9". H/CTR 6".
 Lamps: Three medium base lamps, each 100w max.



P2096-09



P2097-09

FOUR-LIGHT BATH

P2105-09 Brushed Nickel
P2105-20 Antique Bronze
 Size: 34" W., 8-1/2" ht.
 Extends 9". H/CTR 6".
 Lamps: Three medium base lamps, each 100w max.

TWO-LIGHT FLUSH MOUNT

P3617-09 Brushed Nickel
P3617-20 Antique Bronze
 Size: 14" dia., 9" ht.
 Lamps: Two medium base lamps, each 60w max.



P2105-09



P2105-20

All bath fixtures mount up or down.

JOY

WITH SOPHISTICATED DESIGN STYLING, JOY FEATURES VOLUMINOUS CRUVES FOR A SOFT AND STYLISH PROFILE. JOY IS NOW AVAILABLE IN THE POPULAR ANTIQUE BRONZE FINISH WITH ETCHED WHITE GLASS SHADES FOR A CONTEMPORARY LOOK.

THREE-LIGHT FOYER

P3587-20W Antique Bronze

Size: 14-5/8" dia., 17" ht.

Overall ht. w/chain 104"; wire 12'.

Lamps: Three candelabra base lamps, each 60w max.

THREE-LIGHT INVERTED PENDANT

P3951-20W Antique Bronze

Size: 19-1/2" dia., 24-3/4" ht.

Overall ht. w/chain 114"; wire 12'.

Lamps: Three medium base lamps, each 100w max.

THREE-LIGHT CHANDELIER

P4489-20W Antique Bronze

Size: 20" dia., 16-3/8" ht.

Overall ht. w/chain 103"; wire 12'.

Lamps: Three medium base lamps, each 100w max.



FIVE-LIGHT CHANDELIER

P4490-20W Antique Bronze

Size: 24" dia., 18-7/8" ht.

Overall ht. w/chain 106"; wire 12'.

Lamps: Five medium base lamps, each 100w max.



P4490-20W



NINE-LIGHT CHANDELIER

P4492-20W Antique Bronze
Two-tier. 120" chain.
Size: 28" dia., 27-3/4" ht. Overall
ht. w/chain 115"; wire 15'.
Lamps: Nine medium base lamps,
each 100w max.

TWELVE-LIGHT CHANDELIER

P4497-20W Antique Bronze
Two-tier.
Size: 38" dia., 39-5/8" ht. Overall
ht. w/chain 174-1/2"; wire 15'.
Lamps: Nine medium base lamps,
each 75w max.

P4497-20W



MINI-PENDANT

P5270-20W Antique Bronze
Size: 6" dia., 7" ht.
Overall ht. w/chain or stem 94";
wire 12'.
Lamp: One medium base lamp,
100w max.

P5270-20W



P5270-20W



*Joy fixtures can be stem or chain hung.
All fixtures come with 72" of chain and
two 6" stems.*

WITH SOPHISTICATED DESIGN STYLING, JOY FEATURES VOLUMINOUS CRUVES FOR A SOFT AND STYLISH PROFILE. JOY IS NOW AVAILABLE IN THE POPULAR ANTIQUE BRONZE FINISH WITH ETCHED WHITE GLASS SHADES FOR A CONTEMPORARY LOOK.

JOY

ONE-LIGHT BATH

P2000-20W Antique Bronze
Size: 6" W., 9-1/2" ht.
Extends 7". H/CTR 6".
Lamp: One medium base lamp, 100w max.

TWO-LIGHT BATH

P2001-20W Antique Bronze
Size: 14" W., 7-5/8" ht.
Extends 8-1/8". H/CTR 4-1/8".
Lamps: Two medium base lamps, each 100w max.

THREE-LIGHT BATH

P2002-20W Antique Bronze
Size: 22" W., 7-5/8" ht.
Extends 8-1/8". H/CTR 4-1/8".
Lamps: Three medium base lamps, each 100w max.

FOUR-LIGHT BATH

P2003-20W Antique Bronze
Size: 30" W., 7-5/8" ht.
Extends 8-1/8". H/CTR 4-1/8".
Lamps: Four medium base lamps, each 100w max.

TWO-LIGHT SEMI-FLUSH

P3855-20W Antique Bronze
Size: 13-3/8" dia., 9-5/8" ht.
Lamps: Two medium base lamps, each 100w max.



P3855-20W



P2000-20W



P2001-20W



P2002-20W



P2003-20W

Bravo

A CURRENT, TRULY TRANSITIONAL STYLE IS ACHIEVED WITH BRAVO'S FREE FLOWING ARMS THAT ARE GRACEFULLY SUSPENDED WITH FLUTED SHAPED GLASS. THE POPULAR BRAVO COLLECTION NOW COMES WITH THE ANTIQUE BRONZE FINISH WITH WHITE ETCHED GLASS SHADES.



THREE-LIGHT FOYER

P3821-20W Antique Bronze
 Size: 18" dia., 21-1/2" ht.
 Overall ht. w/chain 96"; wire 12'.
 Lamps: Three medium base lamps, each 100w max.

THREE-LIGHT INVERTED PENDANT

P3912-20W Antique Bronze
 Size: 21" dia., 23-1/2" ht.
 Overall ht. w/chain 98"; wire 12'.
 Lamps: Three medium base lamps, each 100w max.

THREE-LIGHT CHANDELIER

P4621-20W Antique Bronze
 Size: 23" dia., 20-1/8" ht.
 Overall ht. w/chain 95"; wire 12'.
 Lamps: Three medium base lamps, each 100w max.

FOUR-LIGHT CHANDELIER

P4622-20W Antique Bronze
 Size: 23" dia., 20-1/8" ht.
 Overall ht. w/chain 95"; wire 12'.
 Lamps: Four medium base lamps, each 100w max.

FIVE-LIGHT CHANDELIER

P4623-20W Antique Bronze
 Size: 27" dia., 23" ht.
 Overall ht. w/chain 97"; wire 12'.
 Lamps: Five medium base lamps, each 100w max.



All bath fixtures mount up or down.

Bravo

ONE-LIGHT FOYER

P3969-20W Antique Bronze

Size: 20" dia., 30-3/8" ht.

Overall ht. w/chain 105-1/2"; wire 12'.

Lamp: One medium base lamp, 100w max.

NINE-LIGHT CHANDELIER

P4625-20W Antique Bronze

Two-tier.

Size: 32" dia., 31" ht.

Overall ht. w/chain 106"; wire 15'.

Lamps: Nine medium base lamps, each 100w max.

TWELVE-LIGHT CHANDELIER

P4687-20W Antique Bronze

Three-tier.

Size: 38" dia., 44" ht.

Overall ht. w/chain 119"; wire 15'.

Lamps: Twelve medium base lamps, each 75w max.

MINI-PENDANT

P5300-20W Antique Bronze

Includes 6' of chain and two 6" stems.

Size: 7-1/4" dia., 6-1/2" ht.

Overall ht. w/chain or stem 94"; wire 10'.


Lamp: One medium base lamp, 100w max.



A CURRENT, TRULY TRANSITIONAL STYLE IS ACHIEVED WITH BRAVO'S FREE FLOWING ARMS THAT ARE GRACEFULLY SUSPENDED WITH FLUTED SHAPED GLASS. THE POPULAR BRAVO COLLECTION NOW COMES WITH AN ANTIQUE BRONZE FINISH WITH WHITE ETCHED GLASS SHADES.

ONE-LIGHT BATH

P2004-20W Antique Bronze
 Size: 7-1/4" W., 9" ht.
 Extends 8-3/4". H/CTR 4-1/2".
 Lamp: One medium base lamp, 100w max.



P2004-20W

TWO-LIGHT BATH

P2005-20W Antique Bronze
 Size: 17" W., 8-1/2" ht.
 Extends 8-3/4". H/CTR 6".
 Lamps: Two medium base lamps, each 100w max.



P2005-20W

THREE-LIGHT BATH

P2006-20W Antique Bronze
 Size: 26-3/4" W., 8-1/2" ht.
 Extends 8-3/4". H/CTR 6".
 Lamps: Three medium base lamps, each 100w max.



P2006-20W

FOUR-LIGHT BATH

P2007-20W Antique Bronze
 Size: 37-1/4" W., 8-1/2" ht.
 Extends 8-3/4". H/CTR 6".
 Lamps: Four medium base lamps, each 100w max.



P2007-20W

FIVE-LIGHT BATH

P2016-20W Antique Bronze
 Size: 46-1/4" W., 8-7/8" ht.
 Extends 8-3/4". H/CTR 6-3/8".
 Lamps: Five medium base lamps, each 100w max.




P2016-20W

All bath fixtures mount up or down.

INSPIRED BY ANCIENT ARMILLARY SPHERES, EQUINOX CONTINUES TO EXPAND WITH FIXTURE OPTIONS WITHIN ITS FAMILY.

Equinox



FIVE-LIGHT PENDANT
P3841-126 Burnished Silver
P3841-20 Antique Bronze
Size: 22" dia., 24-3/8" ht.
Overall ht. w/chain 99-1/2";
wire 15'.
Lamps: Five candelabra base
lamps, each 60w max.

For additional Legend, Orbitz and Clayton fixtures see Catalog 131.

Orbitz

RECTILINEAR TUBING, FRAME AND RING STYLING WHITE ETCHED GLASS SHADES.



FIVE-LIGHT CHANDELIER
P4659-09 Brushed Nickel
 Size: 23-1/4" dia., 18-1/2" ht. Overall ht. w/chain 85"; wire 15'.
 Lamps: Five medium base lamps, each 100w max.

Includes one 6" stem, four 12" stems and 6 links of chain.

Clayton

CLASSIC VINTAGE STYLING MEETS MINIMALISTIC DESIGN. FRESH LOOK USING AUTHENTIC ARCHING ARMS, TURNKEY DECORATIVE DETAILS AND PLEATED DRUM SHADES IN WHITE LINEN FABRIC.




NINE-LIGHT CHANDELIER
P4712-84 Espresso
 Two-tier. Shades do not pivot.
 Size: 37-1/4" dia., 33" ht. Overall ht. w/chain 156"; wire 15'.
 Lamps: Nine medium base lamps, each 100w max.

Legend

A TWO-LIGHT ISLAND FIXTURE AND A TWELVE-LIGHT CHANDELIER ROUND OUT THE POPULAR FAMILY KNOWN FOR ITS STUNNING, SCULPTED GLASS. SMOOTH AND POLISHED ON THE OUTSIDE, YET DISPLAYING A SUBTLE, NATURE-INSPIRED PATTERN ON THE INSIDE, THIS ELEGANT DESIGN APPEARS TO COME ALIVE WHEN ILLUMINATED.



P4254-20



TWO-LIGHT LINEAR CHANDELIER

P4254-09 Brushed Nickel

P4254-20 Antique Bronze

Size: 36" L., 14" W., 16-7/8" ht.

Overall ht. w/chain 92"; wire 15'.

Lamps: Two medium base lamps, each 100w max.

P4653-09

TWELVE-LIGHT CHANDELIER

P4653-09 Brushed Nickel

P4653-20 Antique Bronze

Size: 44" dia., 44-1/8" ht. Overall ht. w/chain 168"; wire 15'.

Lamps: Twelve medium base lamps, each 75w max.



P4653-20



Invite

THIS NEW ADDITION TO THE INVITE COLLECTION HAS ELEGANT, ICONIC SCROLL ARMS, DUAL LAYER ETCHED GLASS SURROUNDED BY MYLAR DRUM SHADES AND CLEAR CYLINDRICAL FINIALS.

TWELVE-LIGHT CHANDELIER

P4725-09 Brushed Nickel

P4725-20 Antique Bronze

Three-tier.

Size: 49" dia., 38" ht. Overall ht. w/chain 161"; wire 15'.

Lamps: Twelve medium base lamps, each 75w max.



Replay

SMOOTH FORMS, LINEAR DETAILS, WHITE GLASS AND A PLEASING ELEGANT FRAME ENHANCE A SIMPLIFIED MODERN LOOK.

NINE-LIGHT CHANDELIER

P4726-31 Black

P4726-104 Polished Nickel

Size: 25-1/2" dia., 28" ht. Overall ht. w/chain 104"; wire 15'.

Lamps: Nine medium base lamps, each 100w max.



Inspire

UPDATED TRADITIONAL FEEL WITH FLOWING OVAL ARMS AND OFF WHITE LINEN DRUM SHADES.

SIX-LIGHT CHANDELIER

P4739-09 Brushed Nickel

P4739-20 Antique Bronze

Size: 30" dia., 22" ht.

Overall ht. w/chain 97"; wire 10'.

Lamps: Six candelabra base lamps, each 60w max.



Gather

SIMPLIFIED FRAME WITH
UPDATED STYLIND AND ELEGANT
ETCHED GLASS SHADES.

TWO-LIGHT CONVERTIBLE

P3748-09 Brushed Nickel

P3748-20 Antique Bronze

Size: 12-1/2" dia., 10-3/8" ht.

Overall ht. w/chain 24"; wire 6'.

Lamps: Two medium base
lamps, each 100w max.

THREE-LIGHT CHANDELIER

P4734-09 Brushed Nickel

P4734-20 Antique Bronze

Size: 19-1/2" dia., 16-1/2" ht.

Overall ht. w/chain 61"; wire 8'.

Lamps: Three medium base
lamps, each 100w max.

FIVE-LIGHT CHANDELIER

P4735-09 Brushed Nickel

P4735-20 Antique Bronze

Size: 23" dia., 17-1/2" ht.

Overall ht. w/chain 62"; wire 8'.

Lamps: Five medium base
lamps, each 100w max.

P3748-20



P3748-09



P4735-09



P4734-09



P4735-20



P4734-20



Heart

IRON ARMS THAT MIMIC THE SHAPE OF A HEART AND ETCHED GLASS SHADES GIVE A CURVACEOUS, FLOWING STYLE.

THREE-LIGHT INVERTED PENDANT

P3955-15 Polished Chrome
Size: 17-3/4" dia., 21-3/4" ht.
Overall ht. w/chain 66"; wire 96".
Lamps: Three medium base lamps, each 100w max.

THREE-LIGHT CHANDELIER

P4664-15 Polished Chrome
Size: 22" dia., 18" ht.
Overall ht. w/chain 63"; wire 96".
Lamps: Three medium base lamps, each 100w max.

FIVE-LIGHT CHANDELIER

P4666-15 Polished Chrome
Size: 25-1/2" dia., 19-1/8" ht.
Overall ht. w/chain 63"; wire 96".
Lamps: Five medium base lamps, each 100w max.

MINI-PENDANT

P5131-15 Polished Chrome
Includes 42" chain and two 6" stems.
Size: 6" dia., 6" ht.
Overall ht. w/chain or stem 63"; wire 96".
Lamp: One medium base lamp, 100w max.

P4664-15



P4666-15



P3955-15




P5131-15



Markor


A POPULAR PENDANT COLLECTION WITH LED AND CFL SOURCES NOW AVAILABLE. NEW COLORS INCLUDE CRIMSON, KHAKI, SUMMER LINEN AND HARVEST LINEN.



10" DRUM SHADES
Acrylic bottom diffuser.
For use with P5101 and P5198 only.
Size: 10" dia., 8" ht.
P8828-30 Summer Linen
P8828-39 Crimson
P8828-56 Khaki
P8828-59 Harvest Linen



P8828-30
shown with pendant kit (sold separately)



P8828-39
shown with pendant kit (sold separately)



P8828-56
shown with pendant kit (sold separately)




P8828-59
shown with pendant kit (sold separately)

16" DRUM SHADE
Acrylic bottom diffuser.
For use with P5101 or P5107 and P5198 or P5199 (see Catalog 131).
Size: 16" dia., 10" ht.
P8829-30 Summer Linen
P8829-39 Crimson
P8829-56 Khaki
P8829-59 Harvest Linen



P8829-30
shown with pendant kit (sold separately)



P8829-39
shown with pendant kit (sold separately)



P8829-56
shown with pendant kit (sold separately)



P8829-59
shown with pendant kit (sold separately)

For more Markor shade and stem kit options see Catalog 131.

22" DRUM SHADES

Acrylic bottom diffuser.
For use with P5101 or P5107 and
P5198 or P5199 (see Catalog 131).
Size: 22" dia., 10" ht.

P8830-30 Summer Linen

P8830-39 Crimson

P8830-56 Khaki

P8830-59 Harvest Linen



Pendant Kits for Markor Shades

Shades and pendant kits are sold separately. 9" and 10" shades can be used only with pendant kit P5101 or P5198 (see Catalog 131). 16" and 22" shades can be used with pendant kit P5101, P5107, P5198 or P5199 (see Catalog 131 for incandescent versions).

ONE-LIGHT LED PENDANT KIT

P5198-0930K9 Brushed Nickel

P5198-2030K9 Antique Bronze

One-light pendant kit for all Markor shades. 3000K. 90+ CRI. 1211 lumens.

Size: 5-3/4" dia., 5-3/8" ht. Overall ht. w/stem and lamps 62"; wire 10'.

Lamp: One 17w LED module included.

ONE-LIGHT CFL PENDANT KIT

P5101-09 Brushed Nickel

P5101-20 Antique Bronze

One-light pendant kit for use with all Markor shades.

Size: 1-5/8" dia., 5-5/8" ht. Overall ht. w/stem and lamps 68"; wire 10'.

Lamp: One 26w GU24 CFL lamp.

THREE-LIGHT CFL PENDANT KIT

P5107-09 Brushed Nickel

P5107-20 Antique Bronze

Three-light pendant kit for use with most 16" and 22" shades only.

Size: 4-3/4" dia., 6-1/4" ht. Overall ht. w/stem and lamps 68"; wire 10'.

Lamps: Three 26w GU24 CFL lamps.



THIS UNIQUELY SHAPED PENDANT HAS A BRUSHED NICKEL FINISH WITH A WHITE LINEN INTERIOR FOR OPTIMAL LIGHT OUTPUT.

Kiss LED

LED MINI-PENDANT

P5186-0930K9 Brushed Nickel
 Size: 5" dia., 5-7/8" ht.
 Overall ht. w/stem 72";
 wire 10'.
 Lamp: One 9w LED module included.



LED PENDANT

P5187-0930K9 Brushed Nickel
 Size: 10" dia., 10-3/4" ht.
 Overall ht. w/stem 77";
 wire 10'.
 Lamp: One 17w LED module included.



AVANT

LED MINI-PENDANT

P5072-0930K9 Brushed Nickel
P5072-2030K9 Antique Bronze
 Size: 9" dia., 4-3/4" ht.
 Overall ht. w/stem 125";
 wire 10'.
 Lamp: One 9w LED module included.



A MODERN LED PENDANT FEATURING CONTRASTING TEXTURES, INCLUDING SANDBLASTED GLASS INSIDE ACCENTED BY A POLISHED OUTSIDE SURFACE.



- 120V AC Replaceable LED module
- 17w: 1211 lumens , 71.2 lumens/watt
- 9w: 623 lumens, 69.2 lumens/watt
- 3000K color temperature
- TM-21 60,000 hr. life
- Dimmable to 10% with many ELV type dimmers
- 90+ CRI
- CA Title 24 Compliant

Includes one 6" stem, four 12" stems and 6 links of chain.

A BOLD AND STRIKING PRISMATIC GLASS SHADE IS THE FOCAL POINT IN THESE LED PENDANTS. FEATURING A SLEEK BRUSHED NICKEL CAP AND STEMS HIGHLIGHTING THE INDUSTRIAL STYLING. BOTTOM OF FIXTURE IS ENCLOSED WITH ETCHED GLASS DIFFUSER.

PRISMATIC



LED MINI-PENDANT

P5075-0930K9 Brushed Nickel
 Size: 9-1/8" dia., 8-1/4" ht.
 Overall ht. w/stem 74";
 wire 10'.
 Lamp: One 9w LED module included.



LED PENDANT

P5143-0930K9 Brushed Nickel
 Size: 12-3/4" dia., 10-7/8" ht.
 Overall ht. w/stem 77"; wire 10'.
 Lamp: One 9w LED module included.



LED LINEAR CHANDELIER

P4715-0930K9 Brushed Nickel
 Size: 9-1/8" W., xx" L., 12-5/8" ht.
 Overall ht. w/stem xx"; wire 15'.
 Lamps: Three 9w LED modules included.



- 120V AC Replaceable LED module
- 623 lumens per module
- 69.2 lumens/watt
- 3000K color temperature
- TM-21 60,000 hr. life
- Dimmable to 10% with many ELV type dimmers
- 90+ CRI
- CA Title 24 Compliant



Includes two 6" stems, one 12" stem, one 15" stem and a 90° swivel.

Pure LED

CORD HUNG LED PENDANTS WITH DESIGN ORIENTED DETAILS. ANTIQUE BRONZE AND WHITE HAVE AN ANODIZED GOLD INTERIOR. PISTACHIO AND BRUSHED NICKEL HAVE A GLOSS WHITE INTERIOR.

Simple LED

THIS SIMPLE LED PENDANT HAS THE LED MODULE TUCKED INSIDE A FROSTED ACRYLIC SHADE. A LIGHT COMMERCIAL PENDANT IDEAL FOR RESTAURANT, BAR AND HOTEL APPLICATIONS.

LED PENDANT

P5175-0930K9 Brushed Nickel
P5175-2030K9 Antique Bronze with Natural Brass Accents
P5175-3030K9 White with Natural Brass Accents
P5175-7930K9 Pistachio
 Size: 6-1/2" dia., 8-7/8" ht.
 Overall ht. w/cord 130";
 wire 10'.
 Lamp: One 9w LED module included.



LED PENDANT

P5176-0930K9 Brushed Nickel
P5176-2030K9 Antique Bronze
 Size: 5-7/8" dia., 8-5/8" ht.
 Overall ht. w/cord 130";
 wire 10'.
 Lamp: One 9w LED module included.



- 120v AC, replaceable module
- 9w - 623 lumens, 69.2 lumens/watt
- 3000K color temperature
- TM-21 60,000 hr. life
- Dimmable to 10% with many ELV type dimmers
- 90+ CRI
- CA Title 24 Compliant

BLISS

THREE-LIGHT FLUSH MOUNT
FROM THE BLISS COLLECTION
FEATURES OVERSIZED K9
BEADS IN AN ANTIQUE
BRONZE IRON FRAME.

THREE-LIGHT SEMI-FLUSH

P3990-20 Antique Bronze

Size: 17" dia., 10" ht.

Lamps: Three candelabra base
lamps, each 60w max.



P3990-20

Flourish

CONTRASTING ARTISANAL GLASS AND TEXTURED
SHADE ARE FEATURED IN FLOURISH'S NEW
CONVERTIBLE, SEMI-FLUSH FIXTURE. CLEAR
GEOMETRIC GLASS SHAPES WITH SMALLER BEADS
AND LARGER PENDANTS ADORN THE COGNAC FINISH.

THREE-LIGHT CONVERTIBLE

P3710-72 Cognac

Size: 15-1/8" dia., 17-1/2" ht.

Overall ht. w/chain 57"; wire 10'.

Lamps: Three candelabra base
lamps, each 60w max.



P3710-20

STATUS

THE WHITE LINEN SHADE, SOFT
FROSTED GLASS DIFFUSER AND K9
GLASS ACCENT OF THIS TWO-LIGHT
FLUSH MOUNT COMPLETE THIS
SOPHISTICATED LOOK.

TWO-LIGHT FLUSH MOUNT

P3402-15 Polished Chrome

Size: 13" dia., 8" ht.

Lamps: Two medium base lamps,
each 60w max.



P3402-15

*For more fixtures in the Bliss, Flourish and Status
collections please see Catalog 131.*

Legend

THE TWO-LIGHT FLUSH MOUNT OF THE LEGEND COLLECTION FEATURES SMOOTH GLASS ON THE OUTSIDE WITH A SUBTLE, NATURE-INSPIRED PATTERN ON THE INSIDE.



TWO-LIGHT FLUSH MOUNT
P3993-09 Brushed Nickel
P3993-20 Antique Bronze
Size: 14" dia., 7-1/2" ht.
Lamps: Two medium base lamps, each 60w max.



P3993-20



P3993-09

Merge

THE CLEAN, MODERN SILHOUETTE OF THIS SEMI FLUSH CONVERTIBLE BLENDS WITH A GLASS SHADE AND IRON ELEMENTS.

SEMI-FLUSH CONVERTIBLE
P3589-20 Antique Bronze
Size: 14-5/8" dia., 12" ht.
Overall ht. w/chain 51"; wire 10'.
Lamps: Two medium base lamps, each 100w max.



P3589-20



P3589-20



For additional fixtures in the Legend and Merge collections see Catalog 131.

FLEET

FLEET FLUSH MOUNT AND CONVERTIBLE FIXTURES ARE COMPRISED OF A DISTINCT CIRCULAR RING INSET INTO THE ETCHED WHITE GLASS SHADE.

TWO-LIGHT FLUSH MOUNT

P3670-09 Brushed Nickel
P3670-15 Polished Chrome
Size: 13" dia., 6-5/8" ht.
Lamps: Two medium base lamps, each 60w max.

TWO-LIGHT CONVERTIBLE

P3669-09 Brushed Nickel
P3669-15 Polished Chrome
Comes with two 12" stems and 6 links of chain.
Size: 13" dia., 10-3/8" ht.
Overall ht. w/chain 53"; wire 10'.
Lamps: Two medium base lamps, each 100w max.



P3669-15



P3669-09



P3669-15



P3670-09



P3669-09



P3670-15

See pages 108-109 for matching bath fixtures.

THE WEAVER COLLECTION COMBINES LINEN DRUM SHADES WITH A LINEN GLASS DIFFUSER TO OFFER A WARM FEEL IDEAL FOR RESIDENTIAL APPLICATIONS, INCLUDING KITCHENS AND LAUNDRY ROOMS, AS WELL AS LIGHT COMMERCIAL ENVIRONMENTS.

Weaver LED



P3610-0930K9

P3610-2030K9

P3611-0930K9

P3611-2030K9

P3612-0930K9

P3612-2030K9

ONE-LIGHT FLUSH MOUNT

P3610-0930K9 Brushed Nickel

P3610-2030K9 Antique Bronze

Size: 10" dia., 3-1/2" ht.

Lamp: One 17w integral LED module included.



TWO-LIGHT FLUSH MOUNT

P3611-0930K9 Brushed Nickel

P3611-2030K9 Antique Bronze

Size: 16" dia., 4" ht.

Lamps: Two 17w integral LED modules included.



THREE-LIGHT FLUSH MOUNT

P3612-0930K9 Brushed Nickel

P3612-2030K9 Antique Bronze

Size: 22" dia., 4-1/2" ht.

Lamps: Three 17w integral LED modules included.



- 120V AC Replaceable LED module
- 1211 lumens per module
- 71.2 lumens/watt
- 3000K color temperature
- TM-21 60,000 hr. life
- Dimmable to 10% with many ELV type dimmers
- 90+ CRI
- CA Title 24 Compliant

Portal LED

A SERIES OF FLUSH MOUNTS ADORNED WITH INDUSTRIAL-INSPIRED ACCENTS AND ETCHED GLASS.



ONE-LIGHT FLUSH MOUNT

P3658-0930K9 Brushed Nickel

P3658-2030K9 Antique Bronze

Size: 11" dia., 3-3/4" ht.

Lamp: One 17w integral LED module included.



ONE-LIGHT FLUSH MOUNT

P3659-0930K9 Brushed Nickel

P3659-2030K9 Antique Bronze

Size: 14" dia., 5-1/2" ht.

Lamp: One 17w integral LED module included.



- 120V AC Replaceable LED module
- 1211 lumens per module
- 71.2 lumens/watt
- 3000K color temperature
- TM-21 60,000 hr. life
- Dimmable to 10% with many ELV type dimmers
- 90+ CRI
- CA Title 24 Compliant



P3658-2030K9

Maier LED

THE MAIER LED FLUSH MOUNTS FEATURE AN ACRYLIC DIFFUSER WHICH TWISTS INTO THE FRAME SO THERE ARE NO EXPOSED FASTENERS FOR A CLEAN MODERN LOOK.

- 120v AC, replaceable module
- 1211 lumens, 71.2 lumens/watt
- 3000K color temperature;
- 90+ CRI
- TM-21 60,000 hr. life
- Dimmable to 10% with many ELV type dimmers
- CA Title 24 Compliant

THREE-LIGHT FLUSH MOUNT

P3675-2030K9 Antique Bronze
P3675-3030K9 White
 Size: 18" dia., 5-1/4" ht.
 Lamps: Three 17w integral LED modules included.



P3675-3030K9

TWO-LIGHT FLUSH MOUNT

P3911-2030K9 Antique Bronze
P3911-3030K9 White
 Size: 14" dia., 4-3/4" ht.
 Lamps: Two 17w integral LED modules included.



P3675-2030K9

ONE-LIGHT FLUSH MOUNT

P3910-2030K9 Antique Bronze
P3910-3030K9 White
 Size: 9" dia., 4-3/8" ht.
 Lamp: One 17w integral LED module included.



P3911-3030K9



P3910-3030K9



P3910-2030K9



P3911-2030K9

See Catalog 131 for Brushed Nickel versions of this LED collection.

Milford LED

ETCHED GLASS SURROUNDED BY A DIE-CAST ALUMINUM FRAME. IDEAL FOR INDOOR AND OUTDOOR APPLICATIONS.

ONE-LIGHT FLUSH MOUNT

P3665-2030K9 Antique Bronze

P3665-3130K9 Black

Size: 8-5/8" dia., 4-1/8" ht.

Lamp: One 17w integral LED module included.



ONE-LIGHT FLUSH MOUNT

P3673-2030K9 Antique Bronze

P3673-3130K9 Black

Size: 10-5/8" dia., 4-7/8" ht.

Lamp: One 17w integral LED module included.



P3665-3130K9



P3665-2030K9



P3673-2030K9



P3673-3130K9

Appeal

SOFT CONTEMPORARY DESIGN FEATURES SQUARE OPAL GLASS.

ONE-LIGHT FLUSH MOUNT

P3991-09 Brushed Nickel

P3991-15 Polished Chrome

P3991-20 Antique Bronze

Size: 7-1/2" sq., 3-1/2" ht.

Lamp: One medium base lamp, 75w max.



P3991-09

THREE-LIGHT FLUSH MOUNT

P3992-09 Brushed Nickel

P3992-15 Polished Chrome

P3992-20 Antique Bronze

Size: 13" sq., 5" ht.

Lamps: Three medium base lamps, each 60w max.



P3991-20



P3991-15



P3992-20



P3992-15



P3992-09

For more sizes of Appeal use Catalog 131.

Incandescent Domes

DOME SHAPED ETCHED
GLASS WITH SOLID TRIM AND
DECORATIVE KNOBS

ONE-LIGHT FLUSH MOUNT

P3924-15ET Polished Chrome
Size: 11-3/8" dia., 5-1/2" ht.
Lamp: One medium
base lamp, 60w max.



P3924-15ET

TWO-LIGHT FLUSH MOUNT

P3925-15ET Polished Chrome
Size: 13-1/4" dia., 5-7/8" ht.
Lamps: Two medium base lamps,
each 75w max.



P3925-15ET

THREE-LIGHT FLUSH MOUNT

P3926-15ET Polished Chrome
Size: 15-1/4" dia., 6-5/8" ht.
Lamps: Three medium base lamps,
each 60w max.



P3926-15ET

SEMI-FLUSH CONVERTIBLE

P3927-15ET Polished Chrome
Size: 13-1/4" dia., 11-3/8" ht.
Overall ht. w/chain 50"; wire 6'.
Lamps: Two medium
base lamps, each 100w max.



P3927-15ET

ONE-LIGHT CFL WALL SCONCE

P7188-30WB White
Etched Glass
Size: 13" W., 5-1/4" ht.
Extends 6-1/2". H/CTR 2-1/2".
Lamp: One 13w GU24 CFL lamp,
included.



P7188-30WB



P3927-15ET



P3410-20WB



P3410-30WB

CFL Fitters

Product No.	Finish	Description	Size	Lamp(s)	
P3408-20WB	Antique Bronze	One-light	7-1/2" dia.,	1 13w GU24	
P3408-30WB	White	One-light	4-3/8" ht.	included	
P3410-20WB	Antique Bronze	Two-light	9-1/4" dia.,	2 13w GU24	
P3410-30WB	White	Two-light	5-1/8" ht.	included	

LED Fitters

Product No.	Finish	Description	Size	Lamp(s)	
P3408-2030K9	Antique Bronze	One-light	7-1/2" dia.,	1 17w integral LED	
P3408-3030K9	White	One-light	4-11/16" ht.	Module included	

PROGRESS



P3408-30WB
P3408-3030K9



P3408-20WB
P3408-2030K9

Melon Glass

Product No.	Finish	Description	Size	Lamp(s)	
P3702-09WB	Brushed Nickel	One-light	11-3/8" dia.,	1 13w GU24	
			6" ht.	included	
P3703-09WB	Brushed Nickel	Two-light	13-1/4" dia.,	2 13w GU24	
			7" ht.	included	
P3704-09WB	Brushed Nickel	Three-light	15-1/4" dia.,	2 13w GU24	
			7-1/2" ht.	included	



P3702-09WB

P3703-09WB

P3704-09WB

Alabaster Glass

Product No.	Finish	Description	Size	Lamp(s)	
P3760-20EBWB	Antique Bronze	Two-light	16-3/4" dia.,	2 18w GU24 CFL.	
			5-1/2" ht.	(included)	
P3764-20EBWB	Antique Bronze	One-light	11-1/2" dia.,	1 13w GU24 CFL.	
			3-3/4" ht.	(included)	
P3765-20EBWB	Antique Bronze	Two-light	14" dia.,	2 13w GU24 CFL.	
			4-3/4" ht.	(included)	

P3764-20EBWB

P3765-20EBWB

P3760-20EBWB

DASH LED

ARCHITECTURALLY MODERN LED SCONCES ARE RELEVANT, INCORPORATES A CREATIVE DESIGN TO SHAPE LIGHT ON THE WALL FOR A DRAMATIC EFFECT.

PROGRESS **LED**



P7163-12930K9

ONE-LIGHT WALL SCONCE

P7163-0930K9 Brushed Nickel with polished chrome accents

P7163-12930K9 Architectural Bronze with natural brass accents

Size: 4-1/2" W., 12-1/2" ht.

Extends 3-1/4". H/CTR 10-1/4".

Lamp: One 9w LED module included.



- 623 lumens per module
- 69.2 lumens/watt
- 3000K color temperature
- Dimmable to 10% with many ELV type dimmers
- 90+ CRI



P7163-0930K9



Archives

THIS TWO-LIGHT LINEAR BATH VANITY FIXTURE OFFERS A VINTAGE ELECTRIC FEEL. CLEAR GLASS SHADES FEATURED ON EITHER SIDE OF THE BACK PLATE ARE ACCENTED BY A TWO-TONE FINISH. MOUNT HORIZONTALLY OR VERTICALLY.

TWO-LIGHT BATH


P2809-20 Antique Bronze with natural brass accents

P2809-81 Antique Nickel with polished chrome accents.

Size: 18-1/2" W., 4-3/4" ht.

Extends 7". H/CTR 2-3/8".

Lamps: Two medium base lamps, each 100w max.



P2809-20
Shown with P7826-01 vintage lamps



P2809-81
Shown with P7826-01 vintage lamps




P2809-20
Shown with P7826-01 vintage lamps

For additional Archives fixtures see Catalog 131.

STREAMING

WITH CLEAN AND UNCLUTTERED FEATURES, STREAMING FEATURES CLEAR, FROSTED GLASS AND A POLISHED CHROME FINISH. FIXTURES CAN BE MOUNTED UP OR DOWN. IN EITHER ORIENTATION, A PEEK OF LIGHT STREAMS FROM THE SHADE.



P2123-15



P2124-15



P2125-15



P2126-15

ONE-LIGHT BATH
P2123-15 Polished Chrome
 Size: 5" W., 5" ht.
 Extends 4-3/4". H/CTR 2-1/2".
 Lamp: One candelabra/krypton
 lamp, 60w max.

TWO-LIGHT BATH
P2124-15 Polished Chrome
 Size: 14" W., 5" ht.
 Extends 4-3/4". H/CTR 2-1/2".
 Lamps: Two candelabra/
 krypton lamps, each 60w max.

THREE-LIGHT BATH
P2125-15 Polished Chrome
 Size: 22" W., 5" ht.
 Extends 4-3/4". H/CTR 2-1/2".
 Lamps: Three candelabra/
 krypton lamps, each 60w max.

FOUR-LIGHT BATH
P2126-15 Polished Chrome
 Size: 30" W., 5" ht.
 Extends 4-3/4". H/CTR 2-1/2".
 Lamps: Four candelabra/krypton
 lamps, each 60w max.

All bath fixtures mount up or down.



P7807-01 lamp recommended.

Rush

ONE-LIGHT BATH

P2715-09 Brushed Nickel

P2715-20 Antique Bronze

Size: 8-5/8" W., 4-1/2" ht.

Extends 7-7/8". H/CTR 2-1/4".

Lamp: One G9 halogen lamp, 60w max.



P2715-09

TWO-LIGHT BATH

P2716-09 Brushed Nickel

P2716-20 Antique Bronze

Size: 16" W., 4-1/2" ht.

Extends 4-7/8". H/CTR 2-1/4".

Lamps: Two G9 halogen lamps, each 60w max.



P2715-20

THREE-LIGHT BATH

P2717-09 Brushed Nickel

P2717-20 Antique Bronze

Size: 24" W., 4-1/2" ht.

Extends 4-7/8". H/CTR 2-1/4".

Lamps: Three G9 halogen lamps, each 60w max.

FOUR-LIGHT BATH

P2718-09 Brushed Nickel

P2718-20 Antique Bronze

Size: 32" W., 4-1/2" ht.

Extends 4-7/8". H/CTR 2-1/4".

Lamps: Four G9 halogen lamps, each 60w max.



P2718-20




P2718-09



P7818-01 lamp recommended.

A COMPACT LINEAR BATH AND VANITY COLLECTION WITH BOTH MODERN AND NATURAL HIGHLIGHTS. ETCHED OPAL GLASS AND DUAL FINISHES – ANTIQUE BRONZE WITH NATURAL BRASS HIGHLIGHTS AND BRUSHED NICKEL WITH POLISHED CHROME HIGHLIGHTS.



P2717-09



P2717-20




P2716-20



P2716-09

All bath fixtures mount up or down.

Mingle



P2162-20



P2162-09




P2163-09



P2163-20

MINGLE FEATURES A DECORATIVE METAL FRAME WITH ALTERNATING CIRCULAR SHAPES. THE SOFTLY PATTERNED LIGHT SETS THE RIGHT MOOD FOR A VARIETY OF BATH AND VANITY SETTINGS. ANTIQUE BRONZE WITH NATURAL PARCHMENT GLASS OR BRUSHED NICKEL WITH ETCHED PARCHMENT GLASS.



P2164-20



P2164-09

ONE-LIGHT BATH

P2161-09 Brushed Nickel
P2161-20 Antique Bronze
 Size: 5-5/8" W., 7-1/4" ht.
 Extends 6-1/4". H/CTR 2-7/8".
 Lamp: One medium base lamp, 100w max.

TWO-LIGHT BATH

P2162-09 Brushed Nickel
P2162-20 Antique Bronze
 Size: 15" W., 7-1/4" ht.
 Extends 6-1/4". H/CTR 2-7/8".
 Lamps: Two medium base lamps, each 100w max.

THREE-LIGHT BATH

P2163-09 Brushed Nickel
P2163-20 Antique Bronze
 Size: 23-7/8" W., 7-1/4" ht.
 Extends 6-1/4". H/CTR 2-7/8".
 Lamps: Three medium base lamps, each 100w max.

FOUR-LIGHT BATH

P2164-09 Brushed Nickel
P2164-20 Antique Bronze
 Size: 32-3/4" W., 7-1/4" ht.
 Extends 6-1/4". H/CTR 2-7/8".
 Lamps: Four medium base lamps, each 100w max.



P2161-20



P2161-09

All bath fixtures mount up or down.

Callison



P2176-15

P2176-09

TWO-LIGHT BATH

P2176-09 Brushed Nickel
P2176-15 Polished Chrome
Size: 17-7/8" W., 9" ht.
Extends 7-1/8". H/CTR 2-1/4".
Lamps: Two medium base
lamps, each 100w max.



Shown: P2117-09 bath fixture.

ONE-LIGHT BATH

P2175-09 Brushed Nickel
P2175-15 Polished Chrome
Size: 5-3/4" W., 9" ht.
Extends 7-1/8". H/CTR 3-1/4".
Lamp: One medium base
lamp, 100w max.

THREE-LIGHT BATH

P2177-09 Brushed Nickel
P2177-15 Polished Chrome
Size: 24" W., 9" ht.
Extends 7-1/8". H/CTR 2-1/4".
Lamps: Three medium base
lamps, each 100w max.

FOUR-LIGHT BATH

P2178-09 Brushed Nickel
P2178-15 Polished Chrome
Size: 33-1/8" W., 9" ht.
Extends 7-1/8". H/CTR 2-1/4".
Lamps: Four medium base
lamps, each 100w max.

COMPRISED OF BEAUTIFUL SQUARE GLASS AND A DETAILED PROFILE, CALLISON'S FINE DETAILS ADD SHADOW LINES AND CREATE CONTOURS WITHIN THE FIXTURE. THE DESIGN OFFERS AESTHETIC AND FUNCTIONAL BENEFITS – WITH UNIFORM LIGHT OUTPUT AND REDUCED GLARE. COORDINATES WITH DELTA® ASHLYN FAUCETS.



All bath fixtures mount up or down.

NATURALLY INSPIRED GLASS COMPLEMENTS THE ARCHING IRONWORK IN THE CLUB VANITY COLLECTION.

THE CHIC COMBINATION SERVES AS A PERFECT COMPANION TO DARKER WOOD FURNISHINGS WITHIN THE BATH AREA. FEATURES -20 ANTIQUE BRONZE FINISH.

Club



P2055-20



P2058-20



P2057-20



P2056-20

ONE-LIGHT BATH

P2055-20 Antique Bronze
Size: 6-7/8" W., 17-5/8" ht.
Extends 9-5/8". H/CTR 10-1/4".
Lamp: One medium base lamp, 100w max.

TWO-LIGHT BATH

P2056-20 Antique Bronze
Size: 16" W., 10" ht.
Extends 8-1/2". H/CTR 7-7/8".
Lamps: Two medium base lamps, each 100w max.

THREE-LIGHT BATH

P2057-20 Antique Bronze
Size: 25-1/8" W., 10" ht.
Extends 8-1/2". H/CTR 7-7/8".
Lamps: Three medium base lamps, each 100w max.

FOUR-LIGHT BATH

P2058-20 Antique Bronze
Size: 34-3/8" W., 10" ht.
Extends 8-1/2". H/CTR 7-7/8".
Lamps: Four medium base lamps, each 100w max.

One light mounts in up position only. Balance can mount up or down.

OFFERING UPSCALE, TRADITIONAL DESIGN – WITH A TOUCH OF ELEGANCE – DAZZLE VANITY IS IDEAL FOR USE IN TODAY'S MONOCHROMATIC AND REFINED INTERIORS.

DAZZLE

WITH A CLASSIC SHADE PROFILE AND -09 BRUSHED NICKEL FINISH, THE DAZZLING GLASS CREATES AN INVITING SHIMMER.

ONE-LIGHT BATH

P2050-09 Brushed Nickel
Size: 6-7/8" W., 17-5/8" ht.
Extends 9-5/8". H/CTR 10-1/4".
Lamp: One medium base lamp, 100w max.

TWO-LIGHT BATH

P2051-09 Brushed Nickel
Size: 16" W., 10" ht.
Extends 8-1/2". H/CTR 7-7/8".
Lamps: Two medium base lamps, each 100w max.

THREE-LIGHT BATH

P2052-09 Brushed Nickel
Size: 25-1/8" W., 10" ht.
Extends 8-1/2". H/CTR 7-7/8".
Lamps: Three medium base lamps, each 100w max.

FOUR-LIGHT BATH

P2053-09 Brushed Nickel
Size: 34-3/8" W., 10" ht.
Extends 8-1/2". H/CTR 7-7/8".
Lamps: Four medium base lamps, each 100w max.



P2051-09



P2052-09



P2053-09



P2050-09

One light mounts in up position only. Balance can mount up or down.

Radiance

ONE-LIGHT BATH

P2169-09 Brushed Nickel
P2169-15 Polished Chrome
P2169-139 Rubbed Bronze
Size: 5-1/2" W., 8-3/4" ht.
Extends 7". H/CTR 6-3/8".
Lamp: One medium base
lamp, 100w max.



P2170-09

TWO-LIGHT BATH

P2170-09 Brushed Nickel
P2170-15 Polished Chrome
P2170-139 Rubbed Bronze
Size: 15-3/8" W., 8-3/4" ht.
Extends 7". H/CTR 6-3/8".
Lamps: Two medium base
lamps, each 100w max.



P2170-15



P2170-139

THREE-LIGHT BATH

P2171-09 Brushed Nickel
P2171-15 Polished Chrome
P2171-139 Rubbed Bronze
Size: 24" W., 8-3/4" ht.
Extends 7". H/CTR 6-3/8".
Lamps: Three medium base
lamps, each 100w max.



P2171-139

FOUR-LIGHT BATH

P2172-09 Brushed Nickel
P2172-15 Polished Chrome
P2172-139 Rubbed Bronze
Size: 32-3/4" W., 8-3/4" ht.
Extends 7". H/CTR 6-3/8".
Lamps: Four medium base
lamps, each 100w max.



P2171-15

VINTAGE-INSPIRED CLEAR RIBBED CLASS FINISHED WITH A METAL TRIM RING OFFERS A ROMANTIC EFFECT FOR THE BATH AND VANITY AREA. THREE FINISH OPTIONS PAIR NICELY WITH POPULAR PLUMBING FIXTURES. THE RUBBED BRONZE FINISH COMPLEMENTS DELTA® OIL RUBBED BRONZE (OB).



P2169-09



P2169-15



P2169-139



P2172-139



P2172-09



P2171-09

All bath fixtures mount up or down.

Fuller



P2756-15



P2756-20

ONE-LIGHT BATH

P2756-15 Polished Chrome

P2756-20 Antique Bronze

Size: 6" W., 8-5/8" ht.

Extends 7". H/CTR 5-5/8".

Lamp: One medium base lamp, 100w max.

TWO-LIGHT BATH

P2771-15 Polished Chrome

P2771-20 Antique Bronze

Size: 14-3/4" W., 8-5/8" ht.

Extends 7". H/CTR 5-5/8".

Lamps: Two medium base lamps, each 100w max.



P2771-20



P2771-15

INDUSTRIAL ELEMENTS WITH MODERN ACCENTS OFFER A BEAUTIFUL EFFECT. ETCHED OPAL GLASS IS SUPPORTED BY TWO KNURLED BOLTS, OFFERING LITTLE DETAILS THAT MAKE A BIG STATEMENT WITHIN THE HOME.

THREE-LIGHT BATH

P2773-15 Polished Chrome
P2773-20 Antique Bronze
 Size: 24" W., 8-5/8" ht.
 Extends 7". H/CTR 5-5/8".
 Lamps: Three medium base lamps, each 100w max.

FOUR-LIGHT BATH

P2774-15 Polished Chrome
P2774-20 Antique Bronze
 Size: 33-1/4" W., 8-5/8" ht.
 Extends 7". H/CTR 5-5/8".
 Lamps: Four medium base lamps, each 100w max.



All bath fixtures mount up or down.

FLEET

ONE-LIGHT BATH

P2165-09 Brushed Nickel

P2165-15 Polished Chrome

Size: 5-1/4" W., 7-1/4" ht.

Extends 6-1/2". H/CTR 4-3/4".

Lamp: One medium base lamp, 100w max.



P2165-09

P2165-15

TWO-LIGHT BATH

P2166-09 Brushed Nickel

P2166-15 Polished Chrome

Size: 14-1/8" W., 7-1/4" ht.

Extends 6-1/2". H/CTR 5".

Lamps: Two medium base lamps, each 100w max.



P2168-09

THREE-LIGHT BATH

P2167-09 Brushed Nickel

P2167-15 Polished Chrome

Size: 24" W., 8-5/8" ht.

Extends 6-1/2". H/CTR 5"..

Lamps: Three medium base lamps, each 100w max.

FOUR-LIGHT BATH

P2168-09 Brushed Nickel

P2168-15 Polished Chrome

Size: 33-1/4" W., 8-5/8" ht.

Extends 6-1/2". H/CTR 5".

Lamps: Four medium base lamps, each 100w max.



P2168-15



See matching close-to-ceiling fixtures on page 85.

A FLEETING SPARKLE OF METAL IS WHAT YOU NOTICE FIRST. EMULATING EUROPEAN FAUCET DESIGNS, FLEET IS COMPRISED OF A DISTINCT DIE CAST ARM AND CUP, HIGHLIGHTED BY ETCHED OPAL GLASS TO COMPLETE THE BATH AND VANITY COLLECTION.



All bath fixtures mount up or down.

A SIMPLE YET ELEGANT SERIES OF MODERN LED WALL FIXTURES. GEOMETRIC FROSTED GLASS SHADES PROVIDE EVENLY DIFFUSED ILLUMINATION FOR VANITY APPLICATIONS.

ACE LED

ONE-LIGHT BATH

P2142-1530K9 Polished Chrome

P2142-2030K9 Antique Bronze

Size: 7" W., 4-3/4" ht.

Extends 4". H/CTR 2-3/4".

Lamp: One integral 9w LED module included.

ADA



TWO-LIGHT BATH

P2143-1530K9 Polished Chrome

P2143-2030K9 Antique Bronze

Size: 15-1/2" W., 4-3/4" ht.

Extends 4". H/CTR 2-3/8".

Lamps: Two integral 9w LED modules included.

ADA



THREE-LIGHT BATH

P2144-1530K9 Polished Chrome

P2144-2030K9 Antique Bronze

Size: 24" W., 4-3/4" ht. Extends 4".

H/CTR 2-3/8".

Lamps: Three integral 9w LED modules included.

ADA



FOUR-LIGHT BATH

P2145-1530K9 Polished Chrome

P2145-2030K9 Antique Bronze

Size: 32-1/2" W., 4-3/4" ht.

Extends 4". H/CTR 2-3/8".

Lamps: Four integral 9w LED modules included.

ADA



P2142-1530K9



P2143-1530K9



P2144-1530K9



P2145-1530K9

- 120V AC Replaceable LED module
- 623 lumens per module
- 69.2 lumens/watt
- 3000K color temperature
- TM-21 60,000 hr. life
- Dimmable to 10% with many ELV type dimmers
- 90+ CRI
- CA Title 24 Compliant



P2142-2030K9



P2143-2030K9



P2144-2030K9



P2145-2030K9



All bath fixtures mount up or down.

Appeal

DISTINCTIVE FORMS HIGHLIGHT SOFT MODERN ACCENTS. ETCHED WHITE GLASS SHADES BALANCE NICELY WITH THE FIXTURE'S FULL BACK PLATE AND SIMPLE SQUARE ARMS. CONTRIBUTES TO A DESIRED SPA-LIKE EFFECT.



ONE-LIGHT BATH

P2700-09 Brushed Nickel
P2700-15 Polished Chrome
P2700-20 Antique Bronze
Size: 5-5/8" W., 6-1/4" ht.
Extends 7-1/4". H/CTR 3-1/8".
Lamp: One medium base lamp, 100w max.

TWO-LIGHT BATH

P2701-09 Brushed Nickel
P2701-15 Polished Chrome
P2701-20 Antique Bronze
Size: 14-5/8" W., 6-1/4" ht.
Extends 7-1/4". H/CTR 3-1/8".
Lamps: Two medium base lamps, each 100w max.

THREE-LIGHT BATH


P2702-09 Brushed Nickel
P2702-15 Polished Chrome
P2702-20 Antique Bronze
Size: 24" W., 6-1/4" ht.
Extends 7-1/4". H/CTR 3-1/8".
Lamps: Three medium base lamps, each 100w max.

FOUR-LIGHT BATH

P2703-09 Brushed Nickel
P2703-15 Polished Chrome
P2703-20 Antique Bronze
Size: 33-1/2" W., 6-1/4" ht.
Extends 7-1/4". H/CTR 3-1/8".
Lamps: Four medium base lamps, each 100w max.



P2700-09



P2700-20




P2703-20



P2703-15



P2702-20



P2700-15



P2702-15



P2702-09



P2701-20



P2701-09



P2701-15



P2703-09

All bath fixtures mount up or down.

Replay



P2131-104



P2131-09



P2158-20



P2158-104

ONE-LIGHT BATH

P2131-09 Brushed Nickel
P2131-20 Antique Bronze
P2131-104 Polished Nickel
 Size: 5-1/8" W., 9-3/4" ht.
 Extends 5-7/8". H/CTR 7-1/4".
 Lamp: One medium base lamp, 100w max.

FOUR-LIGHT BATH

P2160-09 Brushed Nickel
P2160-20 Antique Bronze
P2160-104 Polished Nickel
 Size: 31-1/8" W., 7-7/8" ht.
 Extends 6". H/CTR 5-1/4".
 Lamps: Four medium base lamps, each 100w max.



P2158-09

TWO-LIGHT BATH

P2158-09 Brushed Nickel
P2158-20 Antique Bronze
P2158-104 Polished Nickel
 Size: 13" W., 7-7/8" ht.
 Extends 6". H/CTR 5-1/4".
 Lamps: Two medium base lamps, each 100w max.

THREE-LIGHT BATH

P2159-09 Brushed Nickel
P2159-20 Antique Bronze
P2159-104 Polished Nickel
 Size: 22" W., 7-7/8" ht.
 Extends 6". H/CTR 5-1/4".
 Lamps: Three medium base lamps, each 100w max.



P2160-20

For additional Replay fixtures see Catalog 131.

HIGHLIGHTED BY SIMPLE FORMS, LINEAR DETAILS AND ETCHED OPAL GLASS. A PLEASINGLY ELEGANT FRAME ENHANCES A SIMPLIFIED MODERN LOOK WITHIN THE REPLAY COLLECTION.



P2159-104



P2159-20



P2159-09



P2160-09

All bath fixtures mount up or down.

Signal Bay

SIGNAL BAY IS A FULL COLLECTION OF OUTDOOR FAMILY FIXTURES THAT INCORPORATES NAUTICAL DESIGN ELEMENTS, SUCH AS A SHIP'S FRAME OR A LIGHTHOUSE ON THE SHORE. CLEAR SEEDED GLASS AND AN OIL RUBBED BRONZE FINISH COMPLETE THE LINE.



MEDIUM WALL LANTERN

P5618-108 Oil Rubbed Bronze
Size: 8" W., 12" ht. Extends 10-3/4". H/CTR 6-3/8".
Lamp: One medium base lamp, 100w max.

LARGE WALL LANTERN

P5619-108 Oil Rubbed Bronze
Size: 13-3/8" W., 14-3/4" ht. Extends 13-3/8". H/CTR 6-3/8".
Lamp: One medium base lamp, 100w max.

FLUSH MOUNT

P5638-108 Oil Rubbed Bronze
Size: 12" dia., 8-1/4" ht.
Lamp: One medium base lamp, 100w max.

P5638-108



P5521-108



P5614-108



P5421-108

POST LANTERN

P5421-108 Oil Rubbed Bronze
Size: 10" dia., 16-3/8" ht. Fits 3" post (order separately).
Lamp: One medium base lamp, 100w max.

HANGING LANTERN

P5521-108 Oil Rubbed Bronze
Size: 8" dia., 12-3/4" ht. Overall ht. w/chain 88"; wire 10".
Lamp: One medium base lamp, 100w max.

SMALL WALL LANTERN

P5614-108 Oil Rubbed Bronze
Size: 6" W., 9-1/4" ht. Extends 8-1/4". H/CTR 5-1/2".
Lamp: One medium base lamp, 100w max.

P5618-108



P5619-108

TOWNSHIP

ENJOY THE SIMPLE ELEGANCE OF TRADITIONAL STYLING. TOWNSHIP'S CLEAR BEVELED GLASS AND OIL RUBBED BRONZE FINISH CONTAINS NOTES OF NEW ENGLAND-INSPIRED STYLE FOR THIS CHARMING OUTDOOR LANTERN COLLECTION.



POST LANTERN

P5404-108 Oil Rubbed Bronze
 Size: 8" dia., 22-1/2" ht. Fits 3" post (order separately).
 Lamps: Three candelabra base lamps, each 60w max.

HANGING LANTERN

P5504-108 Oil Rubbed Bronze
 Size: 8" dia., 19-3/8" ht. Overall ht. w/chain 94"; wire 10'.
 Lamps: Three candelabra base lamps, each 60w max.

SMALL WALL LANTERN

P5692-108 Oil Rubbed Bronze
 Size: 5-1/2" W., 14-3/4" ht. Extends 8". H/CTR 3-3/4".
 Lamp: One medium base lamp, 60w max.

MEDIUM WALL LANTERN

P5693-108 Oil Rubbed Bronze
 Size: 6-1/2" W., 17-1/2" ht. Extends 10-1/2". H/CTR 4-1/4".
 Lamps: Two candelabra base lamps, each 60w max.



LARGE WALL LANTERN

P5699-108 Oil Rubbed Bronze
 Size: 8" W., 22" ht. Extends 10-1/2". H/CTR 4-1/4".
 Lamps: Three candelabra base lamps, each 60w max.

Maison

MEDIUM WALL LANTERN

P5754-31 Black
P5754-108 Oil Rubbed Bronze
Size: 7-1/4" W., 20" ht. Extends 10-1/2". H/CTR 10-5/8".
Lamps: Three candelabra base lamps, each 60w max.

LARGE WALL LANTERN

P5755-31 Black
P5755-108 Oil Rubbed Bronze
Size: 8-1/2" W., 23-3/4" ht. Extends 12". H/CTR 13-1/2".
Lamps: Three candelabra base lamps, each 60w max.

HANGING LANTERN

P6532-31 Black
P6532-108 Oil Rubbed Bronze
Size: 7-1/4" dia., 17-7/8" ht. Overall ht. w/chain 93"; wire 10'.
Lamps: Two candelabra base lamps, each 60w max.



P5754-31



P5754-108



P5755-108



P5755-31



P6532-108



P6532-31

MAISON OFFERS ELEGANT FRENCH COUNTRY STYLING FOR A VARIETY OF HOME SETTINGS. CLASSIC AND FORMAL CLEAR WATER SEEDED GLASS COMPLEMENTS TWO FINISH OPTIONS – OIL RUBBED BRONZE AND BLACK.



P5753-31

P5753-108

SMALL WALL LANTERN

P5753-31 Black

P5753-108 Oil Rubbed Bronze

Size: 5-3/4" W., 16-1/4" ht.

Extends 8-5/8". H/CTR 9".

Lamp: One medium base lamp, 100w max.

POST LANTERN

P6432-31 Black

P6432-108 Oil Rubbed Bronze

Size: 7-1/4" dia., 20-5/8" ht. Fits

3" post (order separately).

Lamps: Two candelabra base lamps, each 60w max.



P6432-31



P6432-108

Refuge

A CAPE COD-INSPIRED FRAME PAYS HOMAGE TO A CLASSIC NAUTICAL STYLE. LIGHT OUTPUT AND GEOMETRIC FORMS OFFER VISUAL INTEREST TO OUTDOOR EXTERIORS. CLEAR GLASS WINDOWS ARE PAIRED WITH A UNIQUE UMBER GLASS PANEL.



SMALL WALL LANTERN
P6030-108 Oil Rubbed Bronze
Size: 6-1/2" W., 13-1/4" ht.
Extends 6-7/8". H/CTR 4-1/4".
Lamp: One medium base lamp,
100w max.

MEDIUM WALL LANTERN
P6031-108 Oil Rubbed Bronze
Size: 8" W., 16" ht. Extends
8-1/8". H/CTR 5-3/4".
Lamp: One medium base lamp,
100w max.

LARGE WALL LANTERN
P6032-108 Oil Rubbed Bronze
Size: 10-1/2" W., 21" ht. Extends
10". H/CTR 7-1/2".
Lamp: One medium base lamp,
100w max.

POST LANTERN
P6431-108 Oil Rubbed Bronze
Size: 8" dia., 18-5/8" ht. Fits 3"
post (order separately).
Lamp: One medium base lamp,
100w max.

HANGING LANTERN
P6531-108 Oil Rubbed Bronze
Size: 8" dia., 16" ht. Overall ht. w/
chain 91"; wire 10'.
Lamp: One medium base lamp,
100w max.



Endicott

WITH A CRAFTSMAN-INSPIRED MODERN SILHOUETTE, ENDICOTT OFFERS VISUAL INTEREST. THE ELONGATED FRAME IS ELEGANTLY FINISHED WITH UMBER LINEN GLASS.

POST LANTERN

P5400-20 Antique Bronze
Size: 7-3/8" dia., 17-3/4" ht. Fits 3" post (order separately).
Lamp: One medium base lamp, 100w max.

HANGING LANTERN

P5500-20 Antique Bronze
Size: 7-3/8" dia., 15-1/4" ht.
Overall ht. w/chain 91"; wire 12".
Lamp: One medium base lamp, 100w max.

SMALL WALL LANTERN

P5605-20 Antique Bronze
Size: 7-1/4" W., 10-1/2" ht.
Extends 9-1/2". H/CTR 2-3/4".
Lamp: One medium base lamp, 100w max.

MEDIUM WALL LANTERN

P5610-20 Antique Bronze
Size: 7-1/4" W., 14-1/4" ht.
Extends 9-1/2". H/CTR 3-5/8".
Lamp: One medium base lamp, 100w max.

LARGE WALL LANTERN

P5611-20 Antique Bronze
Size: 8-7/8" W., 12-1/2" ht.
Extends 11". H/CTR 3-5/8".
Lamp: One medium base lamp, 100w max.

EXTRA LARGE WALL LANTERN

P5613-20 Antique Bronze
Size: 8-7/8" W., 18" ht. Extends 11". H/CTR 4-1/2".
Lamp: One medium base lamp, 100w max.



P5605-20



P5500-20



P5610-20



P5613-20



P5610-20



P5400-20

Archives

VINTAGE ELECTRIC DESIGN WITH A DOUBLE SHADE - CLEAR-SEEDED OVAL GLASS SURROUNDS OPAL GLASS AND NATURAL BRASS RODS.



HANGING LANTERN
P5564-20 Antique Bronze
Size: 7-7/8" dia., 12-7/8" ht. Overall
ht. w/chain 79"; wire 15'.
Lamp: One medium base lamp,
100w max.

MEDIUM WALL LANTERN
P5615-20 Antique Bronze
Size: 7-7/8" W., 15-3/8" ht.
Extends 8". H/CTR 3-1/4".
Lamp: One medium base lamp,
100w max.

P5615-20

All stem hung fixtures on this spread include one 6" stem, four 12" stem, and 6 links of chain.

Botta

BOTTA'S STYLING PROVIDES A CASUAL FEEL TO COMPLEMENT INTERIORS AND EXTERIORS WITH VINTAGE FLAIR. FINELY CRAFTED ACCENTS HIGHLIGHT CLEAR SEEDED GLASS AND AN ANTIQUE BRONZE FINISH.

SMALL HANGING LANTERN

P5560-20 Antique Bronze
Size: 6-1/4" dia., 9-3/4" ht. Overall ht. w/chain 76"; wire 15'.
Lamp: One medium base lamp, 100w max.

MEDIUM HANGING LANTERN

P5561-20 Antique Bronze
Size: 7-3/4" dia., 12" ht. Overall ht. w/chain 78"; wire 15'.
Lamp: One medium base lamp, 100w max.

SMALL WALL LANTERN

P6043-20 Antique Bronze
Size: 6-1/4" W., 11-5/8" ht. Extends 6-1/2". H/CTR 8-7/8".
Lamp: One medium base lamp, 100w max.

MEDIUM WALL LANTERN

P6050-20 Antique Bronze
Size: 7-3/4" W., 13-7/8" ht. Extends 8-3/8". H/CTR 11".
Lamp: One medium base lamp, 100w max.



TRADITIONAL / CASUAL

WISH MAXIMIZES AESTHETICS IN OUTDOOR AREAS FOR THOSE WHO DESIRE TO PRESERVE THE EXTERIOR ENVIRONMENT. INCLUDED DARK SKY SHIELD PROVIDES FULL CUT OFF ILLUMINATION OR REMOVE FOR A TRADITIONAL LIGHTING EFFECT.

Wish

ANTIQUE BRONZE FINISH HAS ETCHED UMBER LINEN GLASS. BLACK FINISH HAS ETCHED WHITE LINEN GLASS.

SMALL WALL LANTERN

P6084-20 Antique Bronze

P6084-31 Black

Size: 7" W., 10-3/8" ht. Extends 8-5/8". H/CTR 3-1/8".

Lamp: One medium base lamp, 75w max.

POST LANTERN

P6424-20 Antique Bronze

P6424-31 Black

Dark Sky shield not included.

Size: 9" dia., 15-1/4" ht. Fits 3" post (order separately).

Lamp: One medium base lamp, 100w max.



Dark sky cylinder included, except post lantern.



P6084-20



P6084-31



P6424-20



P6424-31



P6524-31



P6524-20



MEDIUM WALL LANTERN

P6085-20 Antique Bronze

P6085-31 Black

Size: 9" W., 12-1/2" ht. Extends 10-1/2". H/CTR 3-1/8".

Lamp: One medium base lamp, 100w max.

HANGING LANTERN

P6524-20 Antique Bronze

P6524-31 Black

Size: 9" dia., 12-1/2" ht. Overall ht. w/chain 87-1/2"; wire 15'.

Lamp: One medium base lamp, 100w max.



P6085-20



P6085-31

Wish LED

SMALL WALL LANTERN

P6084-2030K9 Antique Bronze
P6084-3130K9 Black
Size: 7" W., 10-3/8" ht. Extends
8-5/8". H/CTR 3-1/8".
Lamp: One integral 9w LED
module included.



P6084-2030K9



P6084-3130K9

POST LANTERN

P6424-2030K9 Antique Bronze
P6424-3130K9 Black
Dark Sky shield not included.
Size: 9" dia., 15-1/4" ht. Fits 3"
post (order separately).
Lamp: One integral 9w LED
module included.



*Dark sky cylinder
included, except post
lantern.*

- 120V AC Replaceable LED module
- 17w: 1211 lumens , 71.2 lumens/watt
9w: 623 lumens, 69.2 lumens/watt
- 3000K color temperature
- TM-21 60,000 hr. life
- Dimmable to 10% with many ELV type
dimmers
- 90+ CRI
- CA Title 24 Compliant



P6524-2030K9



P6524-3130K9

WISH MAXIMIZES AESTHETICS IN OUTDOOR AREAS FOR THOSE WHO DESIRE TO PRESERVE THE EXTERIOR ENVIRONMENT. INCLUDED DARK SKY SHIELD PROVIDES FULL CUT OFF ILLUMINATION OR REMOVE FOR A TRADITIONAL LIGHTING EFFECT.

ANTIQUE BRONZE FINISH HAS ETCHED UMBER LINEN GLASS. BLACK FINISH HAS ETCHED WHITE LINEN GLASS.

MEDIUM WALL LANTERN

P6085-2030K9 Antique Bronze
P6085-3130K9 Black
Size: 9" W., 12-1/2" ht. Extends 10-1/2". H/CTR 3-1/8".
Lamp: One integral 17w LED module included.



HANGING LANTERN

P6524-2030K9 Antique Bronze
P6524-3130K9 Black
Size: 9" sq., 12-1/2" ht. Overall ht. w/chain 87-1/2"; wire 15'.
Lamp: One integral 17w LED module included.



P6524-2030K9



P6524-3130K9



P6085-3130K9



P6085-2030K9

East Haven

EAST HAVEN OFFERS CONTEMPORARY STYLING TO COMPLEMENT A VARIETY OF HOME STYLES. A BLACK OR ANTIQUE BRONZE FRAME CRADLES A SEEDED GLASS SHADE.

SMALL WALL LANTERN

P6073-20 Antique Bronze
P6073-31 Black
Size: 5-3/4" W., 10-3/8" ht.
Extends 7". H/CTR 5-3/4".
Lamp: One medium base lamp,
100w max.



P6073-20



P6073-31

MEDIUM WALL LANTERN

P6074-20 Antique Bronze
P6074-31 Black
Size: 7-1/2" W., 12-3/4" ht.
Extends 9-1/2". H/CTR 7-1/4".
Lamp: One medium base lamp,
100w max.



P6074-31



P6075-20

LARGE WALL LANTERN


P6075-20 Antique Bronze
P6075-31 Black
Size: 9-1/2" W., 15-1/8" ht.
Extends 11-1/2". H/CTR 9-3/4".
Lamp: One medium base lamp,
100w max.



P6074-20



P6075-31



P6525-31

POST LANTERN

P6425-20 Antique Bronze
P6425-31 Black
Size: 7-1/2" dia., 15" ht. Fits 3" post (order separately).
Lamp: One medium base lamp, 100w max.

HANGING LANTERN

P6525-20 Antique Bronze
P6525-31 Black
Size: 7-1/2" dia., 13-3/8" ht.
Overall ht. w/chain 90"; wire 15'.
Lamp: One medium base lamp, 100w max.



P6425-31



P6425-20



P6525-20

East Haven LED

SMALL WALL LANTERN

P6077-2030K9 Antique Bronze

P6077-3130K9 Black

Size: 5-3/4" W., 7-7/8" ht.

Extends 7-1/2". H/CTR 4-3/4".

Lamp: One integral 9w LED module included.



P6077-2030K9



MEDIUM WALL LANTERN

P6078-2030K9 Antique Bronze

P6078-3130K9 Black

Size: 7-1/2" W., 9-3/4" ht.

Extends 9-1/8". H/CTR 4-3/4".

Lamp: One integral 9w LED module included.



P6077-3130K9



LARGE WALL LANTERN

P6079-2030K9 Antique Bronze

P6079-3130K9 Black

Size: 9-1/2" W., 12" ht. Extends

11-1/8". H/CTR 4-3/4".

Lamp: One integral 17w LED module included.



P6078-3130K9

P6078-2030K9



- 120V AC Replaceable LED module
- 17w: 1211 lumens , 71.2 lumens/watt
- 9w: 623 lumens, 69.2 lumens/watt
- 3000K color temperature
- TM-21 60,000 hr. life
- Dimmable to 10% with many ELV type dimmers
- 90+ CRI
- CA Title 24 Compliant

P6079-3130K9

P6079-2030K9



EAST HAVEN OFFERS CONTEMPORARY STYLING TO COMPLEMENT A VARIETY OF HOME STYLES. A BLACK OR ANTIQUE BRONZE FRAME CRADLES A SEEDED GLASS SHADE.

POST LANTERN

P6430-2030K9 Antique Bronze
P6430-3130K9 Black
 Size: 7-1/2" dia., 15" ht. Fits 3" post (order separately).
 Lamp: One integral 9w LED module included.



HANGING LANTERN

P6530-2030K9 Antique Bronze
P6530-3130K9 Black
 Size: 7-1/2" dia., 10-3/8" ht. Overall ht. w/chain 86-1/2"; wire 15'.
 Lamp: One integral 9w LED module included.



DISTRICT'S METAL SHADE OFFERS AN INDUSTRIAL-INSPIRED DESIGN. AVAILABLE IN BOTH INCANDESCENT AND LED VERSIONS, THE VERSATILE VINTAGE FORM CAN BE USED IN INDOOR AND OUTDOOR APPLICATIONS. DARK SKY COMPLIANT.

District



P5622-20
P5622-2030K9



P5622-82
P5622-8230K9



P5623-20
P5623-2030K9



P5623-82
P5623-8230K9

LARGE HANGING LANTERN

P5551-20 Antique Bronze

P5551-82 Metallic Gray

Size: 12" dia., 8-1/4" ht. Overall ht. w/cord 130"; wire 12'.

Lamp: One medium base lamp, 100w max.

MEDIUM HANGING LANTERN

P5535-20 Antique Bronze

P5535-82 Metallic Gray

Size: 8" dia., 6-1/4" ht. Overall ht. w/cord 130"; wire 12'.

Lamp: One medium base lamp, 100w max.

MEDIUM WALL LANTERN

P5622-20 Antique Bronze

P5622-82 Metallic Gray

Size: 8" W., 8-1/4" ht. Extends 10-1/4". H/CTR 4-1/8".

Lamp: One medium base lamp, 100w max.

LARGE WALL LANTERN

P5623-20 Antique Bronze

P5623-82 Metallic Gray

Size: 12" W., 10-1/2" ht. Extends 13-1/4". H/CTR 5".

Lamp: One medium base lamp, 100w max.

District LED

LARGE HANGING LANTERN

P5551-2030K9 Antique Bronze
P5551-8230K9 Metallic Gray
 Size: 12" dia., 8-1/4" ht. Overall ht. w/
 cord 130"; wire 12'.
 Lamp: One 9w LED module included.



MEDIUM HANGING LANTERN

P5535-2030K9 Antique Bronze
P5535-8230K9 Metallic Gray
 Size: 8" dia., 6-1/4" ht. Overall ht.
 w/cord 130"; wire 12'.
 Lamp: One 9w LED module
 included.



MEDIUM WALL LANTERN

P5622-2030K9 Antique Bronze
P5622-8230K9 Metallic Gray
 Size: 8" W., 8-1/4" ht. Extends
 10-1/4". H/CTR 4-1/8".
 Lamp: One 9w LED module
 included.



LARGE WALL LANTERN

P5623-2030K9 Antique Bronze
P5623-8230K9 Metallic Gray
 Size: 12" W., 10-1/2" ht. Extends
 13-1/4". H/CTR 5".
 Lamp: One 9w LED module
 included.



- 120V AC Replaceable LED module
- 623 lumens, 69.2 lumens/watt
- 3000K color temperature
- TM-21 60,000 hr. life
- Dimmable to 10% with many ELV type dimmers
- 90+ CRI
- CA Title 24 Compliant



P5535-20
 P5535-2030K9



P5535-82
 P5535-8230K9



P5551-20
 P5621-2030K9



P5551-82
 P5621-8230K9

Edition

EDITION FEATURES CLEAR WATER GLASS ELEMENTS AND A DIE-CAST ALUMINUM, POWDER COATED FRAME. THE DISTINCT HEXAGONAL SHAPE OFFERS A CLASSICAL STYLE TO CONSIDER FOR UPDATING A HOME'S CURB APPEAL.



P6529-20



SMALL WALL LANTERN

P6070-20 Antique Bronze
Size: 5-1/2" W., 9-1/8" ht.
Extends 6-1/2". H/CTR 2-3/4".
Lamp: One medium base lamp, 100w max.

MEDIUM WALL LANTERN

P6071-20 Antique Bronze
Size: 7-1/8" W., 12-1/2" ht.
Extends 8-1/8". H/CTR 3-1/8".
Lamp: One medium base lamp, 100w max.

LARGE WALL LANTERN

P6072-20 Antique Bronze
Size: 9" W., 15-7/8" ht.
Extends 10". H/CTR 4-1/16".
Lamp: One medium base lamp, 100w max.



P6072-20

POST LANTERN

P6429-20 Antique Bronze
Size: 9" W., 21-7/8" ht. Fits 3" post (order separately).
Lamp: One medium base lamp, 100w max.

HANGING LANTERN

P6529-20 Antique Bronze
Size: 7-1/8" dia., 13" ht.
Overall ht. w/chain 88"; wire 180".
Lamp: One medium base lamp, 100w max.



P6429-20



P6071-20



P6070-20

Essential

WHITE LINEN GLASS IS COMPLETED WITH A POWDER COATED ALUMINUM FRAME AND BLACK FINISH, WHILE AN UMBER LINEN GLASS SHADE COMPLEMENTS THE WARM ANTIQUE BRONZE FINISH.

LARGE WALL LANTERN

P6086-20 Antique Bronze

P6086-31 Black

Size: 10" W., 13-7/8" ht. Extends 11-1/8". H/CTR 2-3/8".

Lamp: One medium base lamp, 100w max.

POST LANTERN

P6412-20 Antique Bronze

P6412-31 Black

Size: 10" dia., 18-3/8" ht. Fits 3" post (order separately).

Lamps: Three candelabra base lamps, each 60w max.

HANGING LANTERN

P6512-20 Antique Bronze

P6512-31 Black

Size: 8" dia., 11-1/2" ht. Overall ht. w/chain 87"; wire 15".

Lamp: One medium base lamp, 100w max.



P6086-31



P6086-20



P6512-20



P6412-20



P6412-31



P6512-31



For additional Essential fixtures see Catalog 131.

FEATURING NAUTICAL UNDERTONES, THE BELL OUTDOOR COLLECTION OFFERS CAGE LIGHTS REMINISCENT OF INDUSTRIAL SPACES. IDEAL FOR USE IN BOTH INTERIOR AND EXTERIOR SETTINGS, THIS LED FIXTURE IS AVAILABLE IN CONVERTIBLE CEILING/PENDANT AND WALL MOUNT OPTIONS.

Bell LED

P6536-13630K9



P6536-20630K9



P6536-13630K9



P6536-2030K9



CEILING/PENDANT

P6536-2030K9 Antique Bronze
P6536-13630K9 Textured Graphite
 Size: 6-5/8" dia., 11-3/8" ht.
 Overall ht. w/chain 77"; wire 12'.
 Lamp: One integral 9w LED module included.



SMALL WALL LANTERN

P5676-2030K9 Antique Bronze
P5676-13630K9 Textured Graphite
 Size: 5-1/2" W., 10-5/8" ht. Extends 7-3/8". H/CTR 3".
 Lamp: One integral 9w LED module included.



P5676-2030K9



P5676-13630K9

- 120V AC Replaceable LED module
- 623 lumens, 69.2 lumens/watt
- 3000K color temperature
- TM-21 60,000 hr. life
- 90+ CRI
- CA Title 24 Compliant

ROBUST AND ENERGY EFFICIENT, LED BULKHEADS ARE A GENERAL-PURPOSE LUMINAIRE. COMPRISED OF A DIE-CAST ALUMINUM FRAME AND POLYCARBONATE DIFFUSER. FITURES ARE IMPACT RESISTANT AND OFFER VARIOUS MOUNTING OPTIONS AND CAN BE WIDELY ADOPTED FOR INDOOR AND OUTDOOR APPLICATIONS.

LED Bulkheads

P3648-3030K9 White
P3648-3130K9 Black
 Size: 9-1/2" W., 4-3/8" ht.
 H/CTR 4-3/4".
 Lamp: One integral 17w LED module included.



P3649-3030K9 White
P3649-3130K9 Black
 Size: 6-1/2" W., 10-1/2" ht.
 Extends 4-1/2". H/CTR 5-1/4".
 Lamp: One integral 9w LED module included.



P3650-3030K9 White
P3650-3130K9 Black
 Size: 9-1/2" dia., 4-1/2" ht.
 H/CTR 4-3/4".
 Lamp: One integral 17w LED module included.



P3647-3030K9 White
P3647-3130K9 Black
 Size: 6-1/2" W., 10-1/2" ht.
 Extends 4-3/8". H/CTR 5-1/4".
 Lamp: One integral 9w LED module included.



- 120V AC Replaceable LED module
- 17w: 1211 lumens , 71.2 lumens/watt
 9w: 623 lumens, 69.2 lumens/watt
- 3000K color temperature
- TM-21 60,000 hr. life
- Dimmable to 10% with many ELV type dimmers
- 90+ CRI
- CA Title 24 Compliant



P3648-3030K9
 shown ceiling-mounted



P3648-3130K9
 shown wall-mounted



P3649-3130K9
 shown wall-mounted



P3649-3030K9
 shown ceiling-mounted



P3647-3030K9
 shown wall-mounted



P3647-3130K9
 shown ceiling-mounted



P3650-3030K9
 shown ceiling-mounted



P3650-3130K9
 shown wall-mounted 135

Security Lighting

THESE LED SWIVEL FLOOD LIGHTS HAVE TEMPERED GLASS AND RUGGED DIE CAST CONSTRUCTION. CAN BE USED AS SINGLE OR MULTIPLE HEADS. ORDER BACKPLATE AND FLOODLIGHT SEPARATELY.

FLOOD LIGHT HEAD

P6342-20/30K Antique Bronze

P6342-28/30K White

P6342-82/30K Metallic Gray

Size: 3-3/4" dia., 5" ht.

Extends 3-1/4".

Lamp: 13w LED

BACK PLATE

P6343-20 Antique Bronze

P6343-28 White

P6343-82 Metallic Gray

Five KO gaskets included. Die

cast aluminum construction.

Size: 4-1/2" dia.

- 1000 lumens
- 3000K color temperature
- 60,000 hr. life
- Wet location listed
- Multi-directional swivel joint



P6342-20/30K9



P6342-20/30K9



P6342-82/30K9



P6343-20



P6343-20
shown with (2) P6342-20/30K heads

LED Slim-Line Surface Mount

P8107-20/30K Antique Bronze
P8107-28/30K White
P8107-31/30K Black
P8107-82/30K Metallic Gray
 Flush mount that can mount into a minimum 2" box.
 Size: 5-1/2" W., 2-3/4"
 Lamp: 12w LED



- Flicker free dimming with many ELV dimmers
- Wet location listed
- 90+ CRI
- 120V input voltage AC
- 60,000 hr. life
- 12w: 630 lumens, 52.5 lumens per watt
- CA Title 24 Compliant



P8107-28/30K9



Bracket for P8107-28/30K9 shown mounted into JBox. JBox not included.



LED Decorative Surface Mount

P8147-09/30K9 Brushed Nickel
P8147-20/30K9 Antique Bronze
P8147-28/30K9 White
P8147-31/30K9 Black
 Round with etched glass
 Size: 7-1/4" dia., 2-3/4" ht.
 Lamp: One 17w LED




- Flicker free dimming with many ELV dimmers
- Wet location listed
- 90+ CRI
- 120V input voltage AC
- 60,000 hr. life
- 17w: 1050 lumens , 63 lumens per watt
- CA Title 24 Compliant



P8147-28/30K9

Splice Box for Undercabinet

P7024-31 Black
 Splice box for Hide-a-Lite 4 LED tape system. Splicer with connection between Romex wire and low voltage cable or between two sections of low voltage cable. Mounting screws included.
 Size: 2" W., 3/4" ht., 1/2" L.



P7024-31



THESE NEW 90 CRI VERSIONS OF THE 6" AND 5" TRIM REPLACE THOSE SHOWN IN CATALOG 131.

LED Recessed Trims

6" NEW CONSTRUCTION or REMODEL TRIMS

P8071-20/30K9-AC1-L07 Antique Bronze
P8071-28/30K9-AC1-L07 White
P8071-31/30K9-AC1-L07 Black
P8071-82/30K9-AC1-L07 Metallic Gray
 Description: 717 lumen, 3000K, 90CRI




P8071-28/30K9-AC1-L07



P8071-20/30K9-AC1-L07



P8071-31/30K9-AC1-L07



P8071-82/30K9-AC1-L07



Includes Edison base socket and Quick-Link connector

- Frosted polycarbonate lens controls direct glare from the LEDs
- Dimmable to 10% with many ELV type dimmers
- 12-watt input power
- Lumen output 717 lumens
- Lumen output and distribution comparable to a 65w BR30 incandescent lamp
- 3000K color temperature
- 90+ CRI
- TM-21 60,000 hours life
- Suitable for use in IC or NON-IC applications
- CSAus listed for wet locations

5" P8061 NEW CONSTRUCTION or REMODEL (TRIMS ONLY)

P8061-20/30K9-AC1-L06 Antique Bronze
P8061-28/30K9-AC1-L06 White
P8061-31/30K9-AC1-L06 Black
P8061-82/30K9-AC1-L06 Metallic Gray
 Description: 683 lumen, 3000K, 90CRI



P8061-28/30K9-AC1-L06



P8061-20/30K9-AC1-L06



P8061-31/30K9-AC1-L06



P8061-82/30K9-AC1-L06



Includes Edison base socket and Quick-Link connector

- LED (Light Emitting Diode) lamp included
- Dimmable to 10% with many ELV type dimmers
- 12-watt input power
- Lumen output 683 lumens
- Lumen output and distribution comparable to 65w BR30 incandescent lamp
- 90+ CRI
- TM-21 60,000 hours life
- Suitable for use in IC or NON-IC applications
- cULus listed for wet locations

P84-LED

Ceiling opening: 5-1/4".
 Plaster frame: 7-7/8" x 10-3/4".
 Recessed depth: 5-1/2".
 Pryouts: 1/2" and 3/4".
 Integral quick link connector mates with P8061 series trims.



RD2 OFFERS THE OPPORTUNITY TO CREATE CLEAN CEILING WITH MINIMAL OBTRUSIVENESS. THE DOWNLIGHT PROVIDES GENERAL, WORKABLE LIGHT OUTPUT IN NEW CONSTRUCTION AND RETROFIT APPLICATIONS SUCH AS – HIGH END RESIDENTIAL, HOSPITALITY AND PROFESSIONAL OFFICES.

2" RD2 Pro-Optic®

2" RD2 NEW CONSTRUCTION HOUSING & TRIM

Ceiling Opening 2-7/8"

Ceiling Thickness 1/2" - 1-1/4"

Pryouts 1/2"

ACCESSORY FOR 2" RD2

Product No. P8556-01

Description IC Box with bar hangars.



P8152-21A/27K9
Clear Alzak®



P8152-28/27K9
White



- 120V high efficiency driver
- 2700K
- TM-21 50,000 hour life*
- 900 lumens
- 21 watts
- 35° distribution
- 95+ CRI
- Suitable for wet locations, non-IC rated
- TRIAC forward phase dimmable to 10%
- 5 year warranty
- Completely accessible from below the ceiling

WALL WASH

P8153-21A/27K9
Clear Alzak®



P8153-28/27K9
White



**Life is reduced to 25,000 hours when used with P8856-01 IC Box.*

Easy Installation



Pull the pre-existing wire below the ceiling and connect to the J-tube assembly through the 1/2" knockout.



Simply slide the J-tube closed until locks into place with the springs on the opposite ends of the assembly.



Squeeze the retention rings inset light engine locking the fixture into place.



Once installed be careful not to leave fingerprints on the reflector.

DARK SKY NIGHTSAVER ACCESSORY SHIELD PROVIDES FULL CUTOFF ILLUMINATION FOR SELECTED OUTDOOR LANTERNS (SEE LIST BELOW). DESIGN IS COMPATIBLE WITH ALL MEDIUM BASE LAMPS INCLUDING CFL AND LED.

Nightsaver

SMALL DARK SKY SHIELD

P8400-31 Black
Size: 3-1/4" dia., 6.31" ht.

MEDIUM DARK SKY SHIELD

P8401-31 Black
Size: 4-1/4" dia., 8-3/8" ht.

LARGE DARK SKY SHIELD

P8402-31 Black
Size: 5-1/4" dia., 10-1/4" ht.

DARK SKY COMPATIBILITY LIST

FAMILY NAME	SMALL	MEDIUM	LARGE
ESSENTIAL			
P6059	8400		
P6060		8401	
P6086			8402
P6512		8401	
RESORT			
P5987	8400		
P5988		8401	
P5989			8402
P6504		8401	
P6606			8402
PRAIRIE			
P5763	N/A		
P5764		8401	
P5563		8401	
P5463		8401	



P8400-31



P8402-31



P8401-31

4W 3000K COLOR TEMPERATURE WITH 84+ CRI AND A 120° BEAM SPREAD. LED STEP/WALL LIGHTS ARE AVAILABLE IN A VERTICAL OR HORIZONTAL CONFIGURATION FOR MOUNTING INTO A SINGLE-GANG WALLBOX.

LED Step Lights

P6827-2030K Antique Bronze

P6827-3130K Black
Louvered horizontal step/wall light.
Wet location listed.

Size: 5-1/4" W. , 3-1/2" ht.
Lamp: 4w LED module included.



P6827-2030K



P6827-3130K



P6828-2030K



P6828-3130K

P6828-2030K Antique Bronze

P6828-3130K Black
Louvered vertical step/wall light.
Wet location listed.

Size: 3-1/2" W. , 5-1/4" ht.
Lamp: 4w LED module included.

Vintage Lamps

THESE POPULAR LAMPS ARE AVAILABLE TO GO WITH MANY PROGRESS COLLECTIONS INCLUDING SWING, DRAPER, ARCHIVES AND PENN



P7825-01



P7827-01



P7826-01

P7825-01
40w ST64 Edison E26 medium base. Vintage Amber bulb.
Maximum overall length: 5-7/16"

P7826-01
40w T8 E12 candelabra base. Vintage Amber bulb.
Maximum overall length: 3-1/2"

P7827-01
40w T9 E26 medium base. Vintage Amber bulb.
Maximum overall length: 5-7/16"

LED Replacement Lamp



SKG0905DLED27
G9 5w LED dimmable lamp.
2700K. 350 lumens.
Size: 1-1/2" W., 2-1/5" ht.



SKG0905DLED27

Stem Kit

P8602-09 Brushed Nickel
P8602-20 Antique Bronze
Size: 1/2" dia., 24" ht.
Includes two 6" and one 12" stem.



P8602-20



P8602-09

See Catalog 131 for additional stem and chain options.

PENDANTS HAVE THE POWER TO CHANGE THE LOOK OF A ROOM INSTANTLY. TODAY, THEY CAN BE SEEN IN BATH AND VANITY AREAS, KITCHENS AND FOYERS – IN SINGLES OR IN MULTIPLES OF TWO OR MORE.

PROGRESS LIGHTING'S CANOPY ACCESSORY OFFERS A CONVENIENT WAY TO MOUNT GROUPINGS OF PENDANTS.

Canopy



P8403-09



P8403-20

P8403-09 Brushed Nickel
P8403-20 Antique Bronze
Size: 15-1/2" dia., 1-3/8" ht.

Round canopy kit for three pendants. Maximum pendant width for three lights is 9" each.



P8403-20
shown with P5023-2030K9
mini-pendant



P8403-09
shown with P5032-09
mini-pendant



P8403-09
shown with P5196-09
mini-pendant

THE ROUND ACCESSORY
 ACCOMMODATES 3 FIXTURES,
 WHILE THE LINEAR OPTION CAN
 MOUNT EITHER 2 OR 3 PENDANTS.
 AVAILABLE IN -09 BRUSHED NICKEL
 AND -20 ANTIQUE BRONZE FINISHES.



P8404-09



P8404-20

P8404-09 Brushed Nickel
P8404-20 Antique Bronze
 Size: 23-1/4" L., 4-1/4" ht.

Linear canopy can be used
 with two or three pendants.
 Maximum pendant size for two
 lights is 18" each. Maximum
 pendant size for three lights is
 9" each.



P8404-09
 shown with P5032-09
 mini-pendant



P8404-20
 shown with P5023-2030K9
 mini-pendant



P8404-20
 shown with P5079-20
 mini-pendant

Index



P2000.....	66	P2152.....	23	P2773.....	105	P3659.....	87
P2001.....	66	P2153.....	23	P2774.....	105	P3664.....	32
P2002.....	66	P2158.....	112	P2809.....	92	P3665.....	89
P2003.....	66	P2159.....	112	P2814.....	51	P3667.....	35
P2004.....	69	P2160.....	112	P2820.....	51	P3669.....	85
P2005.....	69	P2161.....	97	P2821.....	51	P3670.....	85
P2006.....	69	P2162.....	97	P2822.....	51	P3671.....	26
P2007.....	69	P2163.....	97	P2851.....	59	P3672.....	2
P2016.....	69	P2164.....	97	P2959.....	59	P3673.....	89
P2051.....	101	P2165.....	106	P2977.....	59	P3674.....	30
P2052.....	101	P2166.....	106	P2978.....	59	P3675.....	88
P2053.....	101	P2167.....	106	P2998.....	59	P3691.....	26
P2056.....	100	P2168.....	106			P3692.....	26
P2057.....	100	P2169.....	102	P3402.....	83	P3700.....	20
P2058.....	100	P2170.....	102	P3408.....	91	P3702.....	91
P2095.....	63	P2171.....	102	P3410.....	91	P3703.....	91
P2096.....	63	P2172.....	102	P3422.....	21	P3704.....	91
P2097.....	63	P2173.....	3	P3507.....	60	P3710.....	83
P2105.....	63	P2174.....	3	P3529.....	5	P3720.....	43
P2123.....	93	P2175.....	98	P3530.....	5	P3739.....	43
P2124.....	93	P2176.....	98	P3531.....	5	P3748.....	76
P2125.....	93	P2177.....	98	P3560.....	60	P3760.....	91
P2126.....	93	P2177.....	98	P3571.....	25	P3764.....	91
P2127.....	45	P2178.....	98	P3587.....	64	P3765.....	91
P2128.....	45	P2700.....	110	P3589.....	84	P3786.....	52
P2129.....	45	P2701.....	110	P3598.....	15	P3787.....	53
P2130.....	45	P2702.....	110	P3601.....	15	P3795.....	53
P2131.....	112	P2703.....	110	P3610.....	86	P3821.....	67
P2142.....	108	P2715.....	94	P3611.....	86	P3841.....	70
P2143.....	108	P2716.....	94	P3612.....	86	P3846.....	56
P2144.....	108	P2717.....	94	P3617.....	62	P3855.....	66
P2145.....	108	P2718.....	94	P3633.....	37	P3887.....	46
P2146.....	39	P2756.....	104	P3644.....	36	P3891.....	48
P2147.....	39	P2761.....	55	P3647.....	135	P3905.....	44
P2148.....	39	P2762.....	55	P3648.....	135	P3910.....	88
P2149.....	39	P2763.....	55	P3649.....	135	P3911.....	88
P2150.....	23	P2764.....	55	P3650.....	135	P3912.....	67
P2151.....	23	P2771.....	104	P3658.....	87	P3924.....	90

P3925.	90	P4626.	58	P4741.	53	P5180.	11	P5754.	116	P6827.	140
P3926.	90	P4653.	73	P4743.	54	P5186.	80	P5755.	116	P6828.	140
P3927.	90	P4654.	62	P4745.	43	P5187.	80			P6828.	140
P3951.	64	P4657.	24	P4746.	42	P5190.	11	P6030.	118		
P3955.	77	P4658.	25	P4747.	43	P5191.	11	P6031.	118	P7042.	137
P3969.	68	P4659.	70	P4748.	44	P5198.	79	P6032.	118	P7143.	24
P3977.	57	P4664.	77	P4749.	47	P5270.	65	P6043.	121	P7149.	17
P3987.	2	P4666.	77	P4750.	49	P5300.	68	P6050.	121	P7159.	10
P3989.	30	P4687.	68	P4751.	50	P5400.	119	P6070.	132	P7163.	92
P3990.	83	P4698.	24	P4752.	48	P5404.	115	P6071.	132	P7165.	27
P3991.	89	P4699.	17			P5421.	114	P6072.	132	P7167.	29
P3992.	89	P4700.	17	P5009.	24	P5500.	119	P6073.	126	P7172.	41
P3993.	84	P4701.	22	P5010.	61	P5504.	115	P6074.	126	P7174.	4
		P4702.	21	P5061.	8	P5521.	114	P6075.	126	P7188.	90
P4035.	60	P4703.	22	P5066.	36	P5535.	130, 131	P6077.	128	P7825.	141
P4036.	61	P4712.	71	P5071.	28	P5551.	130, 131	P6078.	128	P7826.	141
P4037.	61	P4715.	81	P5072.	80	P5560.	121	P6079.	128	P7827.	141
P4248.	19	P4717.	8	P5073.	15	P5561.	121	P6084.	122, 124		
P4254.	72	P4718.	7	P5074.	18	P5564.	120	P6085.	123, 125	P8061.	138
P4321.	62	P4719.	9	P5075.	81	P5605.	119	P6086.	133	P8071.	138
P4458.	57	P4720.	13	P5082.	17	P5606.	3	P6342.	136	P8107.	137
P4459.	57	P4721.	32	P5086.	21	P5610.	119	P6343.	136	P8147.	137
P4489.	64	P4722.	33	P5088.	32	P5611.	119	P6412.	133	P8152.	139
P4490.	64	P4723.	35	P5092.	44	P5613.	119	P6424.	122, 124	P8400.	140
P4492.	65	P4724.	34	P5093.	50	P5614.	114	P6425.	127	P8401.	140
P4497.	65	P4725.	74	P5101.	79	P5615.	120	P6429.	132	P8402.	140
P4612.	36	P4726.	75	P5102.	16	P5618.	144	P6430.	129	P8403.	142
P4613.	36	P4729.	28	P5107.	79	P5619.	114	P6431.	118	P8404.	143
P4614.	38	P4730.	28	P5115.	16	P5621.	31	P6432.	117	P8556.	139
P4615.	4	P4731.	27	P5119.	33	P5622.	130, 131	P6512.	133	P8602.	141
P4616.	4	P4733.	2	P5120.	4	P5623.	130, 131	P6524.	123, 125	P8828.	78
P4617.	40	P4734.	76	P5131.	77	P5638.	114	P6525.	127	P8829.	78
P4618.	41	P4735.	76	P5143.	81	P5664.	52	P6529.	132	P8830.	79
P4619.	58	P4736.	31	P5147.	57	P5676.	134	P6530.	129		
P4621.	67	P4737.	31	P5152.	13	P5692.	115	P6531.	118	SKG09.	141
P4622.	67	P4738.	29	P5168.	13	P5693.	115	P6532.	116		
P4623.	67	P4739.	75	P5175.	82	P5699.	115	P6536.	134		
P4625.	68	P4740.	54	P5176.	82	P5753.	116	P6827.	140		

Every effort has been made to ensure the accuracy of information in this catalog. Progress Lighting reserves the right to make product changes from time to time, without prior notification, which may change the information provided in this catalog. Errors brought to our attention will be corrected in subsequent issues.

UL Listed or Classified or CSA Certified unless otherwise noted.

Bulbs not included with fixtures unless specified. Specifications subject to change without notice.

Metal finishes not specified as "solid" have quality plated or painted finishes.

Finish representations are high resolution digital reproductions, and, while every effort has been made to render colors accurately, they may vary slightly from the actual product, especially hand-painted finishes, due to the nature of hand craftsmanship.

©Progress Lighting 2015
All rights reserved.
International Copyright Secured.

PROGRESS LIGHTING

Progress Lighting

701 Millennium Boulevard
Greenville, South Carolina
29607

12/2015
progresslighting.com

