

Residential & Commercial



Track & Pendant Lighting

LED / Low Voltage / Line Voltage

 **ELCO Lighting**
The Best Choice in Lighting



Track & Pendant Lighting

Track Lighting has become an instant style upgrade to any home or commercial space. ELCO has put a lot of thought and care into the design and manufacture of our Track Lighting line. Our fixtures are a combination of style and sophistication that will match any room design adding drama and style to a define space.

Product Guide

LED Integrated Track Lighting



Integrated LED Track Fixtures 5



Integrated LED Wall Wash Track Fixtures 23

Low/Line Voltage Track Lighting



Low Voltage LED Lamp Track Fixtures 29



Low Voltage Track Fixtures 31



Line Voltage Track Fixtures 46



Wall Wash Track Fixtures 62



CFL & Metal Halide Track Fixtures 63

Tracks & Accessories



Single Circuit Track and Accessories 67



Two Circuit Track and Accessories 70




General Track Accessories 72


Pendant Lighting



LED Pendants 76



Line Voltage Pendants and Accesories 80



Low Voltage Pendants and Accesories 82



Decorative Pendants 84

Extras

Dimmer Compatibility Chart 85

Photometrics 87

ELCO Lighting

Integrated LED Track Lighting



H-Style Standard
(J & L Style Available)

For use with 120V Single
or Two Circuit Tracks

Diecast Aluminum Construction

Standard 38° Beam Angle
(Optional 15° and 24°)

LED COB



INTEGRATED LED



DIMMABLE




90+ CRI




50,000 HOURS

FIXTURES FEATURES




38° Beam Angle
(Optional 15° & 24° lens)



Tilt (90°)

Rotation (358°)

FINISHES



White



Black




Bronze



Nickel

LUMENS



400 lm to 2000 lm


COLOR TEMPERATURE



3000K - 4000K

Integrated LED Track Fixtures

All track fixtures have adjustable adapters to be used with 120V Single or Two Circuit Track



White
ET580DW
800 lm
3000K
10W




Black
ET580DB
800 lm
3000K
10W

LED Albright™



- Diecast adjustable track fixture
- Integrated driver
- 90° tilt, 358° rotation
- 50,000 hours life-span
- 38° Beam Angle Standard. Optional Lenses: EP719C (15°) or EP720C (24°) available

Input Power	10W
Lumens	800
Color Temp.	3000K
CRI	90+
Input Volt	120V
Dimmable	Yes
Beam Angle	38°



White
ET599DW
700 lm
3000K
10W



Black
ET599DB
700 lm
3000K
10W



Bronze
ET599DBZ
700 lm
3000K
10W




Nickel
ET599DN
700 lm
3000K
10W

LED Dutch™




- Traditional aluminum fixture
- Integrated driver
- 90° tilt, 358° rotation
- 50,000 hours life-span

Input Power	10W
Lumens	700
Color Temp.	3000K
CRI	90+
Input Volt	120V
Dimmable	Yes
Beam Angle	40°



Integrated LED Track Fixtures

All track fixtures have adjustable adapters to be used with 120V Single or Two Circuit Track



White
ET598W
710 lm
3000K
10W




Black
ET598B
710 lm
3000K
10W

LED Clove™

- Solid diecast aluminum fixture
- Integrated driver
- 90° tilt, 358° rotation
- 50,000 hours life-span

Input Power	10W
Lumens	710
Color Temp.	3000K
CRI	90+
Input Volt	120V
Dimmable	No
Beam Angle	30°



White
ET578L30W
1075 lm
3000K
14W




Black
ET578L30B
1075 lm
3000K
14W

LED Clove™ II

- Solid diecast aluminum fixture
- Integrated driver
- ETL listed
- 90° tilt, 358° rotation
- 50,000 hours life-span
- 38° Beam Angle Standard. Optional Lenses:
EP719C (15°) or EP720C (24°) available




Input Power	14W
Lumens	1075
Color Temp.	3000K
CRI	90+
Input Volt	120V
Dimmable	Yes
Beam Angle	38°



Integrated LED Track Fixtures

All track fixtures have adjustable adapters to be used with 120V Single or Two Circuit Track



White
ET612DW
800 lm
3000K
10W




Black
ET612DB
800 lm
3000K
10W

LED Transom™ (S)



- Diecast adjustable track fixture
- Integrated driver
- 90° tilt, 358° rotation
- 50,000 hours life-span
- 38° Beam Angle Standard. Optional Lenses: EP719C (15°) or EP720C (24°) available

Input Power	10W
Lumens	800
Color Temp.	3000K
CRI	90+
Input Volt	120V
Dimmable	Yes
Beam Angle	38°



White
ET613DW
1500 lm
3000K
17W




Black
ET613DB
1500 lm
3000K
17W

LED Transom™ (L)




- Diecast adjustable track fixture
- Integrated driver
- 90° tilt, 358° rotation
- 50,000 hours life-span
- 38° Beam Angle Standard. Optional Lenses: EP722C (15°) or EP723C (24°) available

Input Power	17W
Lumens	1500
Color Temp.	3000K
CRI	90+
Input Volt	120V
Dimmable	Yes
Beam Angle	38°



Integrated LED Track Fixtures

All track fixtures have adjustable adapters to be used with 120V Single or Two Circuit Track



White
ET614DW
820 lm
3000K
12W




Black
ET614DB
820 lm
3000K
12W

LED Trilene™ (S)



- Diecast adjustable track fixture
- Integrated driver
- 90° tilt, 358° rotation
- 50,000 hours life-span
- 38° Beam Angle Standard. Optional Lenses: EP724C (15°) or EP725C (24°) available

Input Power	12W
Lumens	820
Color Temp.	3000K
CRI	90+
Input Volt	120V
Dimmable	Yes
Beam Angle	38°



White
ET615DW
1300 lm
3000K
16W




Black
ET615DB
1300 lm
3000K
16W

LED Trilene™ (L)




- Diecast adjustable track fixture
- Integrated driver
- 90° tilt, 358° rotation
- 50,000 hours life-span
- 38° Beam Angle Standard. Optional Lenses: EP726C (15°) or EP727C (24°) available

Input Power	16W
Lumens	1300
Color Temp.	3000K
CRI	90+
Input Volt	120V
Dimmable	Yes
Beam Angle	38°



Integrated LED Track Fixtures

All track fixtures have adjustable adapters to be used with 120V Single or Two Circuit Track



White	White
ET616-27DW	ET616DW
800 lm	800 lm
2700K	3000K
10W	10W

White
ET616-40DW
850 lm
4000K
10W



Black	Black
ET616-27DB	ET616DB
800 lm	800 lm
2700K	3000K
10W	10W


Black
ET616-40DB
850 lm
4000K
10W

LED Stein™ (S)



- Diecast adjustable track fixture
- Integrated driver
- 90° tilt, 358° rotation
- 50,000 hours life-span
- 38° Beam Angle Standard. Optional Lenses: EP719C (15°) or EP720C (24°) available

Input Power	10W
Lumens	800 - 850
Color Temp.	2700K - 4000K
CRI	90+
Input Volt	120V
Dimmable	Yes
Beam Angle	38°



White	White
ET617DW	ET617-40DW
1500 lm	1600 lm
3000K	4000K
18W	18W




Black	Black
ET617DB	ET617-40DB
1500 lm	1600 lm
3000K	4000K
18W	18W

LED Stein™ (L)




- Diecast adjustable track fixture
- Integrated driver
- 90° tilt, 358° rotation
- 50,000 hours life-span
- 38° Beam Angle Standard. Optional Lenses: EP722C (15°) or EP723C (24°) available

Input Power	18W
Lumens	1500 - 1600
Color Temp.	3000K - 4000K
CRI	90+
Input Volt	120V
Dimmable	Yes
Beam Angle	38°



Integrated LED Track Fixtures

All track fixtures have adjustable adapters to be used with 120V Single or Two Circuit Track



White
ET740W
650 lm
3000K
10W
18° Beam



Black
ET740B
650 lm
3000K
10W
18° Beam

White
ET742W
650 lm
3000K
10W
60° Beam

Black
ET742B
650 lm
3000K
10W
60° Beam



White
ET74730W
1050 lm
3000K
17W
42° Beam




Black
ET74730B
1050 lm
3000K
17W
42° Beam

LED Timber™

- Sleek diecast aluminum fixture
- Integrated driver
- 90° tilt, 358° rotation
- 50,000 hours life-span


Input Power	10W
Lumens	650
Color Temp.	3000K
CRI	90+
Input Volt	120V
Dimmable	No
Beam Angle	18° - 60°



LED Windsor™


- 42° standard. Includes 20° lens
- Diecast aluminum fixture
- Integrated driver
- 90° tilt, 358° rotation
- 50,000 hours life-span

Input Power	17W
Lumens	1050
Color Temp.	3000K
CRI	90+
Input Volt	120V
Beam Angle	42°



Integrated LED Track Fixtures

All track fixtures have adjustable adapters to be used with 120V Single or Two Circuit Track



White

3000K, 1000 lm, 15W

ET743DW 15° Beam

ET744DW 25° Beam

ET745DW 38° Beam

ET746DW 60° Beam

3500K, 1050 lm, 15W

ET743-35DW 15° Beam

ET744-35DW 25° Beam

ET745-35DW 38° Beam

ET746-35DW 60° Beam

4000K, 1100 lm, 15W

ET743-40DW 15° Beam

ET744-40DW 25° Beam

ET745-40DW 38° Beam

ET746-40DW 60° Beam

Black

3000K, 1000 lm, 15W

ET743DB 15° Beam

ET744DB 25° Beam

ET745DB 38° Beam

ET746DB 60° Beam

3500K, 1050 lm, 15W

ET743-35DB 15° Beam

ET744-35DB 25° Beam

ET745-35DB 38° Beam

ET746-35DB 60° Beam

4000K, 1100 lm, 15W

ET743-40DB 15° Beam

ET744-40DB 25° Beam

ET745-40DB 38° Beam


ET746-40DB 60° Beam

LED Magnus™




- Modern diecast aluminum fixture
- Integrated driver
- 90° tilt, 358° rotation
- 50,000 hours life-span

Input Power	15W
Lumens	1000 - 1100
Color Temp.	3000K - 4000K
CRI	90+
Input Volt	120V
Dimmable	Yes
Beam Angle	15° - 60°



Integrated LED Track Fixtures

All track fixtures have adjustable adapters to be used with 120V Single or Two Circuit Track



White	White
ET750DW	ET752DW
1000 lm	1000 lm
3000K	3000K
15W	15W
25° Beam	35° Beam




Black	Black
ET750DB	ET752DB
1000 lm	1000 lm
3000K	3000K
15W	15W
25° Beam	35° Beam

LED Celtic™ (S)



- Modern diecast aluminum fixture
- Integrated driver
- 90° tilt, 358° rotation
- 50,000 hours life-span

Input Power	15W
Lumens	1000
Color Temp.	3000K
CRI	90+
Input Volt	120V
Dimmable	Yes
Beam Angle	25° - 35°



White	White
ET753DW	ET754DW
2400 lm	2400 lm
3000K	3000K
30W	30W
15° Beam	28° Beam




Black	Black
ET753DB	ET754DB
2400 lm	2400 lm
3000K	3000K
30W	30W
15° Beam	28° Beam

LED Celtic™ (L)



- Modern diecast aluminum fixture
- Integrated driver
- 90° tilt, 358° rotation
- 50,000 hours life-span

Input Power	30W
Lumens	2400
Color Temp.	3000K
CRI	90+
Input Volt	120V
Dimmable	Yes
Beam Angle	15° - 38°




White
ET755DW
2400 lm
3000K
30W
38° Beam

Black
ET755DB
2400 lm
3000K
30W
38° Beam

Integrated LED Track Fixtures

All track fixtures have adjustable adapters to be used with 120V Single or Two Circuit Track



Adjustable Beam Angle



White
ET756DW
1000 lm
3000K
15W




Black
ET756DB
1000 lm
3000K
15W

LED Angler™ (S)



- Diecast **adjustable beam** track fixture
- Integrated driver
- 90° tilt, 358° rotation
- 50,000 hours life-span
- 18°-50° adjustable beam angle

Input Power	15W
Lumens	1000
Color Temp.	3000K
CRI	90+
Input Volt	120V
Dimmable	Yes
Beam Angle	18° - 50°



Adjustable Beam Angle



White
ET757DW
2000 lm
3000K
30W




Black
ET757DB
2000 lm
3000K
30W

LED Angler™ (L)




- Diecast **adjustable beam** track fixture
- Integrated driver
- 90° tilt, 358° rotation
- 50,000 hours life-span
- 18°-50° adjustable beam angle

Input Power	30W
Lumens	2000
Color Temp.	3000K
CRI	90+
Input Volt	120V
Dimmable	Yes
Beam Angle	18° - 50°



Integrated LED Track Fixtures

All track fixtures have adjustable adapters to be used with 120V Single or Two Circuit Track



Adjustable Beam Angle




LED Bachman™ (S)



- Diecast **adjustable beam** track fixture
- Solid diecast aluminum fixture
- Integrated driver
- 90° tilt, 358° rotation
- 50,000 hours life-span

Input Power	20W
Lumens	1600
Color Temp.	3000K
CRI	90+
Input Volt	120V
Dimmable	Yes
Beam Angle	20° - 50°



Adjustable Beam Angle




LED Bachman™ (L)




- Diecast **adjustable beam** track fixture
- Solid diecast aluminum fixture
- Integrated driver
- 90° tilt, 358° rotation
- 50,000 hours life-span

Input Power	28W
Lumens	2240
Color Temp.	3000K
CRI	90+
Input Volt	120V
Dimmable	Yes
Beam Angle	20° - 50°



Integrated LED Track Fixtures

All track fixtures have adjustable adapters to be used with 120V Single or Two Circuit Track



White	White
ET62530DW	ET62630DW
700 lm	1000 lm
3000K	3000K
10W	13W




Black	Black
ET62530DB	ET62630DB
700 lm	1000 lm
3000K	3000K
10W	13W

LED Cleat™



- Solid diecast aluminum fixture
- Integrated driver
- 90° tilt, 358° rotation
- 50,000 hours life-span
- 38° Beam Angle Standard. Optional Lenses: EP719C (15°) or EP720C (24°) available

Input Power	10W - 13W
Lumens	700 - 1000
Color Temp.	3000K
CRI	90+
Input Volt	120V
Dimmable	Yes
Beam Angle	38°



White	White
ET579L30W	ET579L35W
730 lm	760 lm
3000K	3500K
10W	10W




Black	Black
ET579L30B	ET579L35B
730 lm	760 lm
3000K	3500K
10W	10W

LED Cleat™ Monopoint



- Monopoint diecast fixture
- Integrated driver
- 90° tilt, 358° rotation
- 50,000 hours life-span
- 38° Beam Angle Standard. Optional Lenses: EP719C (15°) or EP720C (24°) available

Input Power	10W
Lumens	730 - 800
Color Temp.	3000K - 4000K
CRI	90+
Input Volt	120V
Dimmable	Yes
Beam Angle	38°




White
ET579L40W
800 lm
4000K
10W

Black
ET579L40B
800 lm
4000K
10W

Integrated LED Track Fixtures

All track fixtures have adjustable adapters to be used with 120V Single or Two Circuit Track



White
ET61830DW
750 lm
3000K
10W




Black
ET61830DB
750 lm
3000K
10W

LED Gordian™ (Mini)



- Solid diecast aluminum fixture
- Integrated driver
- 90° tilt, 358° rotation
- 50,000 hours life-span
- 38° Beam Angle Standard. Optional Lenses: EP719C (15°) or EP720C (24°) available

Input Power	10W
Lumens	750
Color Temp.	3000K
CRI	90+
Input Volt	120V
Dimmable	Yes
Beam Angle	38°



White
ET61930DW
1150 lm
3000K
15W




Black
ET61930DB
1150 lm
3000K
15W

LED Gordian™ (S)




- Solid diecast aluminum fixture
- Integrated driver
- 90° tilt, 358° rotation
- 50,000 hours life-span
- 38° Beam Angle Standard. Optional Lenses: EP719C (15°) or EP720C (24°) available

Input Power	15W
Lumens	1150
Color Temp.	3000K
CRI	90+
Input Volt	120V
Dimmable	Yes
Beam Angle	38°



Integrated LED Track Fixtures

All track fixtures have adjustable adapters to be used with 120V Single or Two Circuit Track



White
ET62030DW **ET62040DW**
2100 lm 2250 lm
3000K 4000K
30W 30W




Black Black
ET62030DB **ET62040DB**
2100 lm 2250 lm
3000K 4000K
30W 30W

LED Gordian™ (M)



- Solid diecast aluminum fixture
- Integrated driver
- 90° tilt, 358° rotation
- 50,000 hours life-span
- 38° Beam Angle Standard. Optional Lenses: EP722C (15°) or EP723C (24°) available

Input Power	30W
Lumens	2100 - 2250
Color Temp.	3000K - 4000K
CRI	90+
Input Volt	120V
Dimmable	Yes
Beam Angle	38°



White White
ET62130DW **ET62140DW**
2900 lm 3150 lm
3000K 4000K
40W 40W




Black Black
ET62130DB **ET62140DB**
2900 lm 3150 lm
3000K 4000K
40W 40W

LED Gordian™ (L)




- Solid diecast aluminum fixture
- Integrated driver
- 90° tilt, 358° rotation
- 50,000 hours life-span
- 38° Beam Angle Standard

Input Power	40W
Lumens	2900 - 3150
Color Temp.	3000K - 4000K
CRI	90+
Input Volt	120V
Dimmable	Yes
Beam Angle	38°



Integrated LED Track Fixtures

All track fixtures have adjustable adapters to be used with 120V Single or Two Circuit Track



White
ET62730DW
600 lm
3000K
8W




Black
ET62730DB
600 lm
3000K
8W

LED Uni™

- Solid aluminum fixture
- Integrated driver
- 90° tilt, 358° rotation
- 50,000 hours life-span



Input Power	8W
Lumens	600
Color Temp.	3000K
CRI	90+
Input Volt	120V
Dimmable	Yes
Beam Angle	38°



White
ET62230DW
700 lm
3000K
10W




Black
ET62230DB
700 lm
3000K
10W

LED Highpoint™ (S)

- Solid diecast aluminum fixture
- Integrated driver
- 90° tilt, 358° rotation
- 50,000 hours life-span
- 38° Beam Angle Standard



Input Power	10W
Lumens	700
Color Temp.	3000K
CRI	90+
Input Volt	120V
Dimmable	Yes
Beam Angle	38°



Hex Louver

For ET622 series

EP322W


White

EP322B

Black

Integrated LED Track Fixtures

All track fixtures have adjustable adapters to be used with 120V Single or Two Circuit Track



White
ET62330DW
1050 lm
3000K
15W




Black
ET62330DB
1050 lm
3000K
15W

LED Highpoint™ (M)



- Solid diecast aluminum fixture
- Integrated driver
- 90° tilt, 358° rotation
- 50,000 hours life-span
- 38° Beam Angle Standard. Optional Lenses:
EP724C (12°) or EP725C (24°) available

Input Power	15W
Lumens	1050
Color Temp.	3000K
CRI	90+
Input Volt	120V
Dimmable	Yes
Beam Angle	38°



White White
ET62430DW **ET62440DW**
1400 lm 1500 lm
3000K 4000K
20W 20W




Black Black
ET62430DB **ET62440DB**
1400 lm 1500 lm
3000K 4000K
20W 20W

LED Highpoint™ (L)



- Solid diecast aluminum fixture
- Integrated driver
- 90° tilt, 358° rotation
- 50,000 hours life-span
- 38° Beam Angle Standard. Optional Lenses:
EP726C (12°) or EP727C (24°) available

Input Power	20W
Lumens	1400 - 1500
Color Temp.	3000K - 4000K
CRI	90+
Input Volt	120V
Dimmable	Yes
Beam Angle	38°



Hex Louver

For ET623 series


EP323W **EP323B**
White Black

For ET624 series

EP324W **EP324B**
White Black

Integrated LED Track Fixtures

All track fixtures have adjustable adapters to be used with 120V Single or Two Circuit Track



White
ET62830DW
 1000 lm
 3000K
 13W




Black
ET62830DB
 1000 lm
 3000K
 13W

LED Tiggap™

- Solid diecast aluminum fixture
- Integrated driver
- 90° tilt, 358° rotation
- 50,000 hours life-span
- 38° Beam Angle Standard. Optional Lenses: EP719C (15°) or EP720C (24°)



Input Power	13W
Lumens	1000
Color Temp.	3000K
CRI	90+
Input Volt	120V
Dimmable	Yes
Beam Angle	38°



Barndoor Accessory

For ET628 series

EP820W **EP820B**
 White Black




Framing Projector

For ET628 series

EP821B
 Black

Integrated LED Track Fixtures

All track fixtures have adjustable adapters to be used with 120V Single or Two Circuit Track



White
ET591W
520 lm
3000K
10W




Black
ET591B
520 lm
3000K
10W

LED Axle™

- Diecast adjustable track fixture
- Integrated driver
- 90° tilt, 358° rotation
- 50,000 hours life-span

Input Power	10W
Lumens	520
Color Temp.	3000K
CRI	90+
Input Volt	120V
Dimmable	No
Beam Angle	40°



WHITE
ET592W
400 lm
3000K
7W





Black
ET593B
400 lm
3000K
10W

LED Contempo™ & Bimini™


- Diecast adjustable track fixture
- Integrated driver
- 90° tilt, 358° rotation
- 35,000 hours life-span

Input Power	7W - 10W
Lumens	400
Color Temp.	3000K
CRI	90+
Input Volt	120V
Dimmable	No
Beam Angle	38°



Integrated LED Track Fixtures

All track fixtures have adjustable adapters to be used with 120V Single or Two Circuit Track




Black
ET594DB
 500 lm
 3000K
 10W

LED Halter™ (S)



- Solid diecast aluminum fixture
- Integrated driver
- 90° tilt, 358° rotation
- 50,000 hours life-span

Input Power	10W
Lumens	500
Color Temp.	3000K
CRI	90+
Input Volt	120V
Dimmable	Yes
Beam Angle	30°




Black
ET597B
 2000 lm
 3000K
 40W

LED Halter™ (L)


- Solid diecast aluminum fixture
- Integrated driver
- 90° tilt, 358° rotation
- 50,000 hours life-span

Input Power	40W
Lumens	2000
Color Temp.	3000K
CRI	90+
Input Volt	120V
Dimmable	No
Beam Angle	30°



Integrated LED Wall Wash Track Fixtures

All track fixtures have adjustable adapters to be used with 120V Single or Two Circuit Track



White ETW4030W	White ETW4040W
2400 lm	2500 lm
3000K	4000K
30W	30W



Black ETW4030B	Black ETW4040B
2400 lm	2500 lm
3000K	4000K
30W	30W

LED Distell™ (12")




- Frosted lens for even light distribution
- 90° tilt, 358° rotation
- 50,000 hours life-span
- Optional front louver available

Input Power	30W
Lumens	2400 - 2500
Color Temp.	3000K - 4000K
CRI	90+
Input Volt	120V
Dimmable	Yes

12" Wall Wash Front Louver

EP555W White	EP555B Black
------------------------	------------------------



White ETW4130W	White ETW4140W
4800 lm	5000 lm
3000K	4000K
60W	60W



Black ETW4130B	Black ETW4140B
4800 lm	5000 lm
3000K	4000K
60W	60W

LED Distell™ (24")




- Frosted lens for even light distribution.
- 90° tilt, 358° rotation
- 50,000 hours life-span
- Optional front louver available

Input Power	60W
Lumens	4800 - 5000
Color Temp.	3000K - 4000K
CRI	90+
Input Volt	120V
Dimmable	Yes



24" Wall Wash Front Louver

EP666W White	EP666B Black
------------------------	------------------------




Integrated LED Wall Wash Track Fixtures

All track fixtures have adjustable adapters to be used with 120V Single or Two Circuit Track



White ETW4230W	White ETW4240W
1400 lm	1550 lm
3000K	4000K
20W	20W




Black ETW4230B	Black ETW4240B
1400 lm	1550 lm
3000K	4000K
20W	20W

LED Pipe™ (12")




- Frosted lens for even light distribution.
- 90° tilt, 358° rotation
- 50,000 hours life-span
- Optional front louver available

Input Power	20W
Lumens	1400 - 1550
Color Temp.	3000K - 4000K
CRI	90+
Input Volt	120V
Dimmable	Yes



White ETW4330W	White ETW4340W
2500 lm	2700 lm
3000K	4000K
40W	40W




Black ETW4330B	Black ETW4340B
2500 lm	2700 lm
3000K	4000K
40W	40W

LED Pipe™ (21")





- Frosted lens for even light distribution.
- 90° tilt, 358° rotation
- 50,000 hours life-span
- Optional front louver available

Input Power	40W
Lumens	2500 - 2700
Color Temp.	3000K - 4000K
CRI	90+
Input Volt	120V
Dimmable	Yes



Integrated LED Wall Wash Track Fixtures

All track fixtures have adjustable adapters to be used with 120V Single or Two Circuit Track




White
ETW4430W
4000 lm
3000K
58W

White
ETW4440W
4300 lm
4000K
58W

LED Pipe™ (27")




- Frosted lens for even light distribution.
- 90° tilt, 358° rotation
- 50,000 hours life-span
- Optional front louver available



Black
ETW4430B
4000 lm
3000K
58W


Black
ETW4440B
4300 lm
4000K
58W

Input Power	58W
Lumens	4000 - 4300
Color Temp.	3000K - 4000K
CRI	90+
Input Volt	120V
Dimmable	Yes



ELCO Lighting

LED Tarbuck™ Linear Track Fixtures



FEATURES



INTEGRATED LED




90+ CRI



50,000 HOURS

FINISHES




White



Black

LUMENS



1400 lm to 1500 lm


COLOR TEMPERATURE



3000K - 4000K

Integrated LED Linear Track Fixtures

All track fixtures have adjustable adapters to be used with 120V Single or Two Circuit Track



White
ETL2130W
1400 lm
3000K
18W

White
ETL2140W
1500 lm
4000K
18W





Black
ETL2130B
1400 lm
3000K
18W

Black
ETL2140B
1500 lm
4000K
18W

LED Tarbuck™

- For use with ELCO single and double circuit track system
- Wide flood beam angle (110°)
- UL Listed

Input Power	18W
Input Volt	120V AC, 60 Hz
Lumens	1400 - 1500
Color Temp.	3000K - 4000K
CRI	90+



ELCO Lighting

Low Voltage Track Lighting

H-Style Standard
(J & L Style Available)




Low Voltage Transformer
For use with 120V Single
or Two Circuit Tracks

ETLD Option has no minimum load transformer


Wide selection of finishes and styles
to match any room design

Fixtures accommodates
LED (ETLD) and Halogen Lamps

FIXTURES FEATURES



Tilt (90°)



Rotation (358°)

FINISHES



White



Black



Bronze



Copper




Gold




Nickel

LAMPS



LED (ETLD)



Halogen

Low Voltage MR16 Track Fixtures (LED & Halogen Lamps)

For use with 12V GU5.3 MR16 LED Lamps or MR16 Halogen Lamps. No minimum load transformer. Lamp not included



White
ETLD526W



Black
ETLD526B

Zeppelin™




DIMMABLE

- For use with 12V GU5.3 MR16 LED lamp or MR16 Halogen lamp (not included)
- No minimum load transformer
- 90° tilt, 358° rotation

Input Power 3W - 50W

Input Volt 120V

Dimmable Yes



White
ETLD528W



Black
ETLD528B



Bronze
ETLD528BZ



Copper
ETLD528CP



Gold
ETLD528G



Nickel
ETLD528N

Cylinder™




DIMMABLE

- For use with 12V GU5.3 MR16 LED lamp or MR16 Halogen lamp (not included)
- No minimum load transformer
- 90° tilt, 358° rotation

Input Power 3W - 50W

Input Volt 120V

Dimmable Yes



All White
ETLD530WW



White
ETLD530W



Black
ETLD530B

Anchor™




DIMMABLE

- For use with 12V GU5.3 MR16 LED lamp or MR16 Halogen lamp (not included)
- No minimum load transformer
- 90° tilt, 358° rotation

Input Power 3W - 50W

Input Volt 120V

Dimmable Yes



Low Voltage MR16 Track Fixtures (LED & Halogen Lamps)

For use with 12V GU5.3 MR16 LED Lamps or MR16 Halogen Lamps. No minimum load transformer. Lamp not included




White
ETLD532W Black
ETLD532B

Hoxton™



- For use with 12V GU5.3 MR16 LED lamp or MR16 Halogen lamp (not included)
- No minimum load transformer
- 90° tilt, 358° rotation

Input Power	50W MAX.
Input Volt	120V
Dimmable	Yes




White
ETLD534W Black
ETLD534B Nickel
ETLD534N

Icicle™



- For use with 12V GU5.3 MR16 LED lamp or MR16 Halogen lamp (not included)
- No minimum load transformer
- 90° tilt, 358° rotation

Input Power	50W MAX.
Input Volt	120V
Dimmable	Yes



White
ETLD558W


Black
ETLD558B

Studio™



- For use with 12V GU5.3 MR16 LED lamp or MR16 Halogen lamp (not included)
- No minimum load transformer
- 90° tilt, 358° rotation

Input Power	50W MAX.
Input Volt	120V
Dimmable	Yes



Low Voltage MR16 Track Fixtures


For use with 120V Single or Two Circuit Track. Lamp not included



Art Deco Gimbal

ET502W White
ET502B Black


- Lamp: 50W 12V MR16
- Lamp not included



High Tech Swivel

ET504W White
ET504B Black
ET504N Nickel


- Lamp: 50W 12V MR16
- Lamp not included



Diecast Gimbal Ring

ET505B Black


- Lamp: 50W 12V MR16
- Lamp not included



Gimbal Ring

ET507W White
ET507B Black


- Lamp: 50W 12V MR16
- Lamp not included



Gimbal Ring

ET526W White / 50W
ET526B Black / 50W
ET526-75W White / 75W
ET526-75B Black / 75W


- Lamp: 12V MR16
- Lamp not included
- Snoot available EP300 (W)(B)



Mini Deco

ET527B Black

- Lamp: 50W 12V MR16
- Lamp not included
- Snoot available EP300 (W)(B)



Low Voltage MR16 Track Fixtures


For use with 120V Single or Two Circuit Track. Lamp not included



High Tech

ET529B Black

- Lamp: 50W 12V MR16
- Lamp not included



Cylinder

ET528W White / 50W

ET528B Black / 50W

ET528G Gold / 50W

ET528N Nickel / 50W


ET528BZ Bronze / 50W

ET528CP Copper / 50W

ET528-75W White / 75W

ET528-75B Black / 75W

- Lamp: 12V MR16
- Lamp not included




Round Back

ET530WW All White

ET530W White

ET530B Black

- Lamp: 50W 12V MR16
- Lamp not included



Soft Square


ET532W White / 50W

ET532B Black / 50W

ET532-75W White / 75W

ET532-75B Black / 75W

- Lamp: 12V MR16
- Lamp not included




Step Cylinder

ET531W White

ET531B Black

ET531WW All White

- Lamp: 42W/50W 12V MR16
- Lamp not included
- Snoot available EP300 (W)(B)



Low Voltage MR16 Track Fixtures


For use with 120V Single or Two Circuit Track. Lamp not included



Clasp

ET534W White / 50W
ET534B Black / 50W
ET534N Nickel / 50W


- Lamp: 12V MR16
- Lamp not included



Mini Deco

ET535W White
ET535B Black


- Lamp: 50W 12V MR16
- Lamp not included
- Snoot available EP300 (W)(B)



Barndoor

ET536W White


- Lamp: 50W 12V MR16
- Lamp not included



Louver

ET537W White
ET537B Black


- Lamp: 50W 12V MR16
- Lamp not included



Mini Projector

ET539W White / 50W
ET539B Black / 50W
ET539-75W White / 75W
ET539-75B Black / 75W


- Lamp: 12V MR16
- Lamp not included



Pinch Back with Barndoor

ET540W White / 50W
ET540B Black / 50W

- Lamp: 12V MR16
- Lamp not included



Low Voltage MR16 Track Fixtures


For use with 120V Single or Two Circuit Track. Lamp not included



Gimbal with Barndoor

ET541W White
ET541B Black


- Lamp: 50W 12V MR16
- Lamp not included



Frosted Stepped Shade Goose Neck

ET544B-R Black/Red Glass
ET544W-R White/Red Glass
ET544B-BL Black/Blue Glass
ET544W-BL White/Blue Glass


- Lamp: 50W 12V MR16
- Track head with 24" goose neck and glass shade
- Lamp not included



High Tech Glass Shade

ET546W White/Frosted Glass
ET546B Black/Frosted Glass


- Lamp: 50W 12V MR16
- Lamp not included



Thin Goose Neck with Solid Shade

ET550W White
ET550B Black
ET550N Nickel


- Lamp: 50W 12V MR16
- Track head with 24" thin goose neck and solid shade
- Lamp not included



Pinch Back

ET547W White / 50W
ET547B Black / 50W
ET547N Nickel / 50W

- Lamp: 12V MR16
- Lamp not included



Framing Projector

For use with ET547

EP821B Black

Low Voltage MR16 Track Fixtures


For use with 120V Single or Two Circuit Track. Lamp not included



Telescopic Antenna

ET548W White
ET548B Black


- Lamp: 42W/50W 12V MR16
- Lamp not included



Wireform

ET554W White
ET554B Black
ET554BZ Bronze


- Lamp: 50W 12V MR16
- Lamp not included



Contempo

ET549B Black


- Lamp: 42W/50W 12V MR16
- Lamp not included



Clasp Globe Shade

ET551B-BL Black/Blue Glass
ET551W-BL White/Blue Glass
ET551B-YL Black/Yellow Glass
ET551W-YL White/Yellow Glass

- Lamp: 50W 12V MR16
- Lamp not included



Low Voltage MR16 Track Fixtures


For use with 120V Single or Two Circuit Track. Lamp not included



Studio

ET558W White
ET558B Black


- Lamp: 50W 12V MR16
- Takes color film membrane
- Lamp not included



Micro Style

ET559B Black


- Lamp: 50W 12V MR16
- Lamp not included



Vertical Gimbal

ET562W White
ET562B Black


- Lamp: 50W 12V MR16
- Lamp not included



Vertical Spot

ET563W White
ET563B Black

- Lamp: 50W 12V MR16
- Lamp not included



Low Voltage PAR36 Track Fixtures

For use with 120V Single or Two Circuit Track. Lamp not included




High Tech Gimbal

ET565W White
ET565B Black

- Lamp: 50W 12V PAR36
- Lamp not included

ET570W White
ET570B Black

- Lamp: 50W 12V AR111
- Lamp not included



MR16 Monopoint Fixtures


Stand alone fixture with round base for mounting onto junction box. Lamp not included



Low Voltage Bi-Pin Monopoint

ET1528W White
ET1528B Black
ET1528N Nickel
ET1528BZ Bronze

- Lamp: 50W 12V MR16 Bi-Pin GU5.3
- Lamp not included



Low Voltage MR16 Builder's Track Kits

Kit Includes: (3) Track Fixtures, (1) 4 Ft. Track, and (1) Floating Canopy. Lamp not included




Gimbal Ring Track Kit

ET566W White

ET566B Black

- Lamp: 50W 12V MR16
- Track Kit Includes: (3) Gimbal Ring Fixtures (ET526), (1) 4' Track, (1) Floating canopy
- Lamps not included




Cylinder Track Kit

ET567W White

ET567B Black

- Lamp: 50W 12V MR16
- Track Kit Includes: (3) Cylinder Fixtures (ET528), (1) 4' Track, (1) Floating canopy
- Lamps not included




Soft Square Track Kit

ET568W White


ET568B Black

- Lamp: 50W 12V MR16
- Track Kit Includes: (3) Soft Square Fixtures (ET532), (1) 4' Track, (1) Floating canopy
- Lamps not included



Low Voltage Fixtures with Stem Extensions

For use with 120V Single or Two Circuit Track. Lamp not included



- For use with 120V Single or Two Circuit Track
- Fixtures with Stem Extensions feature:
 - (1) 12V Solid State Transformer
 - (1) 12"-48" Stem Extension
 - (1) Track Fixture

W = White Extension
B = Black Extension



Gimbal Ring (LED or Halogen)

White

- ETLD526-12W** 12"
- ETLD526-18W** 18"
- ETLD526-24W** 24"
- ETLD526-36W** 36"
- ETLD526-48W** 48"

Black

- ETLD526-12B** 12"
- ETLD526-18B** 18"
- ETLD526-24B** 24"
- ETLD526-36B** 36"
- ETLD526-48B** 48"

- Lamp: 50W MAX 12V GU5.3 MR16 LED or MR16 Halogen
- Fixture: 4 1/2" L x 2 1/8" O.D.
- Lamp not included



Cylinder (LED or Halogen)

White

- ETLD528-12W** 12"
- ETLD528-18W** 18"
- ETLD528-24W** 24"
- ETLD528-36W** 36"
- ETLD528-48W** 48"

Black

- ETLD528-12B** 12"
- ETLD528-18B** 18"
- ETLD528-24B** 24"
- ETLD528-36B** 36"
- ETLD528-48B** 48"

- Lamp: 50W MAX 12V GU5.3 MR16 LED or MR16 Halogen
- Fixture: 4 1/2" L x 2 1/8" O.D.
- Lamp not included

Low Voltage Fixtures with Stem Extensions

For use with 120V Single or Two Circuit Track. Lamp not included



Gimbal Ring

White

ET526-12W 12"
 ET526-18W 18"
 ET526-24W 24"
 ET526-36W 36"
 ET526-48W 48"

Black

ET526-12B 12"
 ET526-18B 18"
 ET526-24B 24"
 ET526-36B 36"
 ET526-48B 48"

- Lamp: 50W 12V MR16
- Fixture: 2" L x 2 1/8" O.D.
- Lamp not included



Round Back

White

ET530-12W 12"
 ET530-18W 18"
 ET530-24W 24"
 ET530-36W 36"
 ET530-48W 48"

Black

ET530-12B 12"
 ET530-18B 18"
 ET530-24B 24"
 ET530-36B 36"
 ET530-48B 48"

- Lamp: 50W 12V MR16
- Fixture: 4" L x 2 1/2" O.D.
- Lamp not included



Cylinder

White

ET528-12W 12"
 ET528-18W 18"
 ET528-24W 24"
 ET528-36W 36"
 ET528-48W 48"

Black

ET528-12B 12"
 ET528-18B 18"
 ET528-24B 24"
 ET528-36B 36"
 ET528-48B 48"

- Lamp: 50W 12V MR16
- Fixture: 3" L x 2 1/4" O.D.
- Lamp not included



Soft Square

White

ET532-12W 12"
 ET532-18W 18"
 ET532-24W 24"
 ET532-36W 36"
 ET532-48W 48"

Black

ET532-12B 12"
 ET532-18B 18"
 ET532-24B 24"
 ET532-36B 36"
 ET532-48B 48"

- Lamp: 50W 12V MR16
- Fixture: 3 1/8" L x 2 1/4" O.D.
- Lamp not included

Low Voltage Fixtures with Stem Extensions

For use with 120V Single or Two Circuit Track. Lamp not included



Studio

White

- ET558-12W 12"
- ET558-18W 18"
- ET558-24W 24"
- ET558-36W 36"
- ET558-48W 48"

Black

- ET558-12B 12"
- ET558-18B 18"
- ET558-24B 24"
- ET558-36B 36"
- ET558-48B 48"

- Lamp: 50W 12V MR16
- Fixture: 4 3/4" L x 3" O.D.
- Lamp not included



Telescopic Antenna

ET548W White

ET548B Black

- Lamp: 50W 12V MR16
- Fixture: 2" O.D.
- Lamp not included



Clasp

White

- ET534-12W 12"
- ET534-18W 18"
- ET534-24W 24"
- ET534-36W 36"
- ET534-48W 48"

Black

- ET534-12B 12"
- ET534-18B 18"
- ET534-24B 24"
- ET534-36B 36"
- ET534-48B 48"

- Lamp: 50W 12V MR16
- Fixture: 2 5/8" L x 3 1/8" O.D.
- Lamp not included



Gimbal Ring

White

- ET565-12W 12"
- ET565-18W 18"
- ET565-24W 24"
- ET565-36W 36"
- ET565-48W 48"

Black

- ET565-12B 12"
- ET565-18B 18"
- ET565-24B 24"
- ET565-36B 36"
- ET565-48B 48"

- Lamp: 50W 12V PAR36
- Fixture: 2 1/2" L x 4 5/8" O.D.
- Lamp not included

Low Voltage MR11 Track Fixtures


For use with 120V Single or Two Circuit Track. Lamp not included



Mini Cylinder

ET128B Black
ET128G Gold


- Lamp: 35W 12V MR11
- Transformer included
- Lamp not included



Mini Soft Square

ET132W White
ET132G Gold


- Lamp: 35W 12V MR11
- Transformer included
- Lamp not included



Mini Octagon

ET169B Black

- Lamp: 35W 12V MR11
- Transformer included
- Lamp not included



Low Voltage MR16 Track 22 Fixtures

Track fixtures can be installed on Line Voltage Track with EP900 Power Pack or Monopoint installation using EP702
Lamps not included




Gimbal Ring

ET926W White

ET926B Black

- Lamp: 50W 12V MR16
- Transformer not included
- Lamp not included




Cylinder

ET928W White

ET928B Black

- Lamp: 50W 12V MR16
- Transformer not included
- Lamp not included




Soft Square

ET932W White

ET932B Black

- Lamp: 50W 12V MR16
- Transformer not included
- Lamp not included



Low Voltage MR16 Track 22 Accessories

For use with Track22 Low Voltage Track Heads



Power Pack

EP900W White

EP900B Black

- 50W transformer for use with Track 22, 12V track fixtures
- For line voltage track only



Monopoint with Transformer

EP702W White

EP702B Black

- 75W monopoint with low voltage transformer
- 12V for use with ET900 series

Line Voltage Halogen Track Fixtures


For use with 120V Single or Two Circuit Track. Lamp not included



Gimbal Ring

ET426W White
ET426B Black


- Lamp: 50W 120V G8 Base MR16 (not included)



Cylinder

ET428W White
ET428B Black


- Lamp: 50W 120V G8 Base MR16 (not included)



Soft Square

ET432W White
ET432B Black

- Lamp: 50W 120V G8 Base MR16 (not included)



Line Voltage Halogen Track Fixtures **Lamp**



G8 Base MR16 Lamp

MR120

- 50W 120V
- Bi-Pin G8 base lamp

ELCO Lighting

Line Voltage GU10 Track Fixtures

(for LED or Halogen Lamps)

H-Style Standard
(J & L Style Available)



For use with 120V Single or Two Circuit Tracks

Wide selection of finishes and styles
to match any room design


Fixtures accommodates
GU10 MR16 LED or Halogen Lamps

Dimmability based on lamp




DIMMABLE

FIXTURES FEATURES



Tilt (90°)



Rotation (358°)

FINISHES



White



Black




Bronze




Nickel

LAMPS



GU10 Halogen
MR120-GU10



GU10 LED
MR120-GU10LD

Line Voltage GU10 Track Fixtures (LED or Halogen)

For use with 120V Single or Two Circuit Track. Lamp not included. Dimmability based on lamp




White
ET1603W Black
ET1603B Nickel
ET1603N

Ossel™



- For use with 120V GU10 MR16 LED lamp or Halogen lamp (not included)
- 90° tilt, 358° rotation
- Dimmability based on lamp

Input Power	50W MAX.
Input Volt	120V
Dimmable	Yes



White
ET1604W




Black
ET1604B

Swivel™



- For use with 120V GU10 MR16 LED lamp or Halogen lamp (not included)
- 90° tilt, 358° rotation
- Dimmability based on lamp

Input Power	50W MAX.
Input Volt	120V
Dimmable	Yes



White
ET1625W




Black
ET1625B

Savoy™



- For use with 120V GU10 MR16 LED lamp or Halogen lamp (not included)
- 90° tilt, 358° rotation
- Dimmability based on lamp

Input Power	50W MAX.
Input Volt	120V
Dimmable	Yes



Line Voltage GU10 Track Fixtures (LED or Halogen)

For use with 120V Single or Two Circuit Track. Lamp not included. Dimmability based on lamp




Bowen™



- For use with 120V GU10 MR16 LED lamp or Halogen lamp (not included)
- 90° tilt, 358° rotation
- Dimmability based on lamp

Input Power	50W MAX.
Input Volt	120V
Dimmable	Yes




Garda™



- For use with 120V GU10 MR16 LED lamp or Halogen lamp (not included)
- 90° tilt, 358° rotation
- Dimmability based on lamp

Input Power	50W MAX.
Input Volt	120V
Dimmable	Yes




Arbor™



- For use with 120V GU10 MR16 LED lamp or Halogen lamp (not included)
- 90° tilt, 358° rotation
- Dimmability based on lamp

Input Power	50W MAX.
Input Volt	120V
Dimmable	Yes



Line Voltage GU10 Track Fixtures (LED or Halogen)

For use with 120V Single or Two Circuit Track. Lamp not included. Dimmability based on lamp



White
ET1632W

Black
ET1632B


Nickel
ET1632N

Crown™



- For use with 120V GU10 MR16 LED lamp or Halogen lamp (not included)
- 90° tilt, 358° rotation
- Dimmability based on lamp

Input Power	50W MAX.
Input Volt	120V
Dimmable	Yes



White
ET1634W

Black
ET1634B


Nickel
ET1634N

Basket™



- For use with 120V GU10 MR16 LED lamp or Halogen lamp (not included)
- 90° tilt, 358° rotation
- Dimmability based on lamp

Input Power	50W MAX.
Input Volt	120V
Dimmable	Yes



White
ET1650W


Black
ET1650B

Noose™



- 18" Goose neck with shade
- For use with 120V GU10 MR16 LED lamp or Halogen lamp (not included)
- 90° tilt, 358° rotation
- Dimmability based on lamp

Input Power	50W MAX.
Input Volt	120V
Dimmable	Yes



Line Voltage GU10 Track Fixtures (LED or Halogen)

For use with 120V Single or Two Circuit Track. Lamp not included. Dimmability based on lamp



White
ET1654W



Nickel
ET1687N



White
ET1728W



White
ET1728W



Black
ET1728B




Nickel
ET1728BZ

Wireform™



- For use with 120V GU10 MR16 LED lamp or Halogen lamp (not included)
- 90° tilt, 358° rotation
- Dimmability based on lamp

Input Power	50W MAX.
Input Volt	120V
Dimmable	Yes




Knute™



- For use with 120V GU10 MR16 LED lamp or Halogen lamp (not included)
- 90° tilt, 358° rotation
- Dimmability based on lamp


Input Power	50W MAX.
Input Volt	120V
Dimmable	Yes



Garda™ Monopoint

- For use with 120V GU10 MR16 LED lamp or Halogen lamp (not included)
- 90° tilt, 358° rotation
- Dimmability based on lamp

Input Power	50W MAX.
Input Volt	120V
Dimmable	Yes



Line Voltage GU10 Track Fixtures (LED or Halogen)

For use with 120V Single or Two Circuit Track. Lamp not included. Dimmability based on lamp



White
ET1671W




Black
ET1671B

Dropper™



- For use with 120V GU10 MR16 LED lamp or Halogen lamp (not included)
- 90° tilt, 358° rotation
- Dimmability based on lamp

Input Power	50W MAX.
Input Volt	120V
Dimmable	Yes



White
ET1673W




Black
ET1673B

Decorative



- For use with 120V GU10 MR16 LED lamp or Halogen lamp (not included)
- 90° tilt, 358° rotation
- Dimmability based on lamp

Input Power	50W MAX.
Input Volt	120V
Dimmable	Yes



Line Voltage GU10 Track Fixtures Lamps



GU10 MR16 Lamp

MR120-GU10

- 50W
- 120V



GU10 MR16 LED Lamp


MR120-GU10LD

- 7W
- 120V, 500 lm, 3000K, CRI 90
- Dimmable

ELCO Lighting

Line Voltage PAR Track Lighting

H-Style Standard
(J & L Style Available)




For use with 120V Single or Two Circuit Tracks

Wide selection of finishes and styles
to match any room design


Fixtures accommodates
PAR20, PAR28, PAR30, PAR38

Its timeless design is perfect for traditional
as well as contemporary interiors

FIXTURES FEATURES



Tilt (90°)



Rotation (358°)

FINISHES



White



Black



Bronze



Copper




Gold



Nickel

LAMPS



(LED or Halogen)

PAR20

PAR28

PAR30

PAR38

Line Voltage 120V PAR Track Fixtures


For use with 120V Single or Two Circuit Track. Lamp not included. Dimmability based on lamp



Gimbal Ring

ET629W White
 ET629B Black
 ET629N Nickel
 ET629BZ Bronze


- Lamp: 50W PAR20
- Lamp not included



Gimbal Ring

ET630W White
 ET630B Black
 ET630N Nickel
 ET630BZ Bronze


- Lamp: 75W PAR30
- Lamp not included
- Louver available EP222 (W)(B)
- Barndoors available EP823



Gimbal Ring

ET631W White
 ET631B Black
 ET631N Nickel
 ET631CP Copper


- Lamp: 150W PAR38
- Lamp not included
- Louver available EP333 (W)(B)
- Barndoors available EP822



Industrial Grade Gimbal

ET633W White
 ET633B Black


- Lamp: 150W PAR38
- With clips for accessories
- Lamp not included
- Louver available EP222 (W)(B)



Flat Back Cylinder

ET634W White
 ET634B Black
 ET634WW All White


- Lamp: 50W R20/PAR20
- Lamp not included



Flat Back Cylinder

ET635W White
 ET635B Black
 ET635WW All White

- Lamp: 75W R30/PAR30
- Lamp not included
- Barndoors available EP822



Line Voltage 120V PAR Track Fixtures


For use with 120V Single or Two Circuit Track. Lamp not included. Dimmability based on lamp



Step Cylinder with Baffle

ET636W White
ET636B Black
ET636WG White/Gold Ring
ET636BG Black/Gold Ring
ET636WW All White


- Lamp: 50W R20/PAR20
- Lamp not included



Step Cylinder with Baffle

ET637W White
ET637B Black
ET637WW All White


- Lamp: 75W R30/PAR30
- Lamp not included
- Barndoors available EP822



Round Back Cylinder

ET638W White
ET638B Black
ET638WW All White


- Lamp: 50W R20/PAR20
- Lamp not included



Round Back Cylinder

ET639W White
ET639B Black
ET639WW All White


- Lamp: 75W R30/PAR30
- Lamp not included
- Barndoors available EP822



Round Back Cylinder

ET640W White
ET640B Black
ET640WW All White


- Lamp: 150W R40/PAR38
- Lamp not included
- Louver available EP444 (W)(B)
- Barndoors available EP422



Universal

ET641W White
ET641B Black

- Lamp: 150W R or PAR
- Lamp not included



Line Voltage 120V PAR Track Fixtures


For use with 120V Single or Two Circuit Track. Lamp not included. Dimmability based on lamp



Universal

ET642W White
 ET642B Black
 ET642N Nickel
 ET642BZ Bronze
 ET642CP Copper


- Lamp: 150W R or PAR
- Lamp not included



Classic Round Back

ET643W White
 ET643B Black
 ET643WG White/Gold Ring
 ET643BG Black/Gold Ring


- Lamp: 50W R20/PAR20
- Lamp not included



Classic Round Back

ET644B Black
 ET644BG Black/Gold Ring


- Lamp: 75W R30/PAR30
- Lamp not included
- Barndoors available EP822



Mini Porcelain

ET646W White


- Lamp: 150W R or PAR
- Lamp not included



Mini Universal

ET647W White
 ET647B Black
 ET647N Nickel
 ET647BZ Bronze
 ET647CP Copper


- Lamp: 75W R or PAR
- Lamp not included



Flat Back Cylinder

ET650W White
 ET650B Black
 ET650WW All White

- Lamp: 150W R40/PAR38
- Lamp not included
- Louver available EP444 (W)(B)
- Barndoors available EP422



Line Voltage 120V PAR Track Fixtures


For use with 120V Single or Two Circuit Track. Lamp not included. Dimmability based on lamp



Wireform

- ET654W White
- ET654B Black
- ET654N Nickel
- ET654BZ Bronze
- ET654CP Copper


- Lamp: 150W PAR38
- Lamp not included



Wireform

- ET655B Black


- Lamp: 75W PAR30
- Lamp not included



Wireform

- ET656B Black
- ET656CP Copper


- Lamp: 75W PAR20
- Lamp not included



Solid PAR Classic

- ET657W White
- ET657B Black
- ET657N Nickel
- ET657BZ Bronze


- Lamp: 50W PAR20
- Lamp not included



Solid PAR Classic

- ET658W White
- ET658B Black
- ET658N Nickel
- ET658BZ Bronze


- Lamp: 75W PAR30
- Lamp not included



Solid PAR Classic

- ET659W White
- ET659B Black
- ET659BZ Bronze

- Lamp: 150W PAR38
- Lamp not included



Line Voltage 120V PAR Track Fixtures


For use with 120V Single or Two Circuit Track. Lamp not included. Dimmability based on lamp



Wall Wash with Louver

ET660B Black


- Lamp: 300W MAX.
T3 Double end quartz
- Lamp not included



Yoke Mount Round Back Cylinder

ET661W White
ET661B Black


- Lamp: 50W R20/PAR20
- Lamp not included



Yoke Mount Round Back Cylinder

ET662W White
ET662B Black


- Lamp: 75W PAR30
- Lamp not included



Wall Wash

ET668W White


- Lamp: 150W T4 ETF
Halogen DC bayonet
- Lamp not included



Wall Wash

ET669B Black


- Lamp: 150W R40/PAR38
- Lamp not included



PAR Classic with Cone

ET673W White
ET673B Black

- Lamp: 50W PAR20
- Lamp not included



Line Voltage 120V PAR Track Fixtures


For use with 120V Single or Two Circuit Track. Lamp not included. Dimmability based on lamp



PAR Classic with Cone

ET674W White
ET674B Black


- Lamp: 75W PAR30
- Lamp not included



PAR Classic with Cone

ET675W White
ET675B Black


- Lamp: 150W PAR38
- Lamp not included



PAR with Mesh

ET676W White
ET676B Black


- Lamp: 50W PAR20
- Lamp not included



PAR with Mesh

ET677W White
ET677B Black
ET677N Nickel


- Lamp: 75W PAR30
- Lamp not included



High Tech PAR with Cone

ET681W White
ET681B Black


- Lamp: 50W PAR20
- Lamp not included



High Tech PAR with Cone

ET682B Black

- Lamp: 75W PAR30
- Lamp not included



Line Voltage 120V PAR Track Fixtures


For use with 120V Single or Two Circuit Track. Lamp not included. Dimmability based on lamp



Front Loading Adjustable Gimbal

ET685W White
ET685B Black


- Lamp: 50W PAR20
- Lamp not included



Front Loading Adjustable Gimbal

ET686W White
ET686B Black


- Lamp: 75W PAR30
- Lamp not included



Front Loading Adjustable Gimbal

ET687W White
ET687B Black


- Lamp: 150W PAR38
- Lamp not included



Mini Universal with Sliding Sleeve

ET690W White
ET690B Black


- Lamp: 50W PAR16, PAR20, PAR30 or 150W PAR38
- Lamp not included



PAR Classic with Cover

ET691W White


- Lamp: 50W PAR20
- Lamp not included



PAR Classic with Cover

ET692W White
ET692B Black

- Lamp: 75W PAR30
- Lamp not included



Line Voltage 120V PAR Track Fixtures


For use with 120V Single or Two Circuit Track. Lamp not included. Dimmability based on lamp



PAR Classic with Cover

ET693G Gold


- Lamp: 150W PAR38
- Lamp not included



PAR Classic

ET694W White
ET694C Chrome
ET694G Gold


- Lamp: 50W PAR20
- Lamp not included



PAR Classic

ET695B Black
ET695G Gold


- Lamp: 75W PAR30
- Lamp not included



PAR Classic

ET696C Chrome
ET696G Gold

- Lamp: 150W PAR38
- Lamp not included



Line Voltage 120V PAR Builder's Track Kits

Kit Includes: (3) Track Fixtures, (1) 4 Ft. Track, and (1) Floating Canopy. Lamp not included. Dimmability based on lamp




Step Cylinder Track Kit

ET665W White

ET665B Black

- Lamp: 75W PAR30
- Track Kit Includes: (3) Step Cylinder Fixtures (ET637)
- Lamps not included




Flat Back Track Kit

ET666W White

ET666B Black

- Lamp: 75W PAR30
- Track Kit Includes: (3) Flat Back Fixtures (ET635)
- Lamps not included




Round Back Track Kit

ET667W White

ET667B Black

- Lamp: 75W PAR30
- Track Kit Includes: (3) Round Back Fixtures (ET639)
- Lamps not included



Line Voltage Track Fixtures


For use with 120V Single or Two Circuit Track. Lamp not included. Dimmability based on lamp



Flat Back Cylinder with Clear Reflector

ET1135W White
ET1135B Black
ET1135WG White w/Gold Ring
ET1135BG Black w/Gold Ring


- Lamp: 26W MAX. Medium Base self ballasted CFL Lamp
- Lamp not included



Round Back Cylinder with Clear Reflector

ET1139W White
ET1139B Black


- Lamp: 26W MAX. Medium Base self ballasted CFL Lamp
- Lamp not included



Solid Cone with Clear Reflector

ET1158W White
ET1158B Black

- Lamp: 26W MAX. GU24 Base self ballasted CFL or LED Lamp
- Lamp not included



Wall Wash Track Fixtures

For use with 120V Single or Two Circuit Track




LED Wall Wash



ETC464B Black

- 70W, 5300 lm, 3500K
- CRI80+
- Dimmable



Wall Wash Fluorescent

ETC424W White


- Lamp: (2) 24W High output T5 fluorescent (not included)
- 24 1/2" Length

ETC439B Black

- Lamp: (2) 39W High output T5 fluorescent (not included)
- 36 1/2" Length

ETC454B Black

- Lamp: (2) 54W High output T5 fluorescent (not included)
- 47" Length




Wall Wash Compact Fluorescent

ETC420W White

ETC420B Black

- Lamp: (1) 26W, 32W, 42W, 4-Pin lamp (not included)



H.I.D. Metal Halide PAR Track Fixtures


For use with 120V Single or Two Circuit Track



PAR20 Metal Halide

ET794W White/20W
ET794B Black/20W
ET795W White/39W
ET795B Black/39W


- Lamp: PAR20 Metal Halide
- Lamp not included



PAR30 Metal Halide

ET796W White/39W
ET796B Black/39W
ET797W White/70W
ET797B Black/70W


- Lamp: PAR30 Metal Halide
- Lamp not included



PAR38 Metal Halide

ET798W White/70W
ET798B Black/70W


- Lamp: PAR38 Metal Halide
- Lamp not included



PAR20 Adjustable Metal Halide

ET734W White
ET734B Black


- Lamp: 39W PAR20 Metal Halide
- Lamp not included



PAR30 Adjustable Metal Halide

ET735W White
ET735B Black


- Lamp: 70W PAR30 Metal Halide
- Lamp not included



PAR38 Adjustable Metal Halide

ET736W White
ET736B Black

- Lamp: 100W PAR38 Metal Halide
- Lamp not included



H.I.D. Metal Halide MR16 Track Fixtures

For use with 120V Single or Two Circuit Track



Decorative Gimbal


ET771W White/20W

ET771B Black/20W

ET772W White/39W

ET772B Black/39W

- Lamp: MR16 Metal Halide GX10 Base
- Lamp not included



Decorative Gimbal


ET773W White/20W

ET773B Black/20W

ET774W White/39W

ET774B Black/39W

- Lamp: MR16 Metal Halide GX10 Base
- Lamp not included






Track Lighting **Accessories**


ELCO Lighting provides a wide range of track lighting accessories to build on or add to any existing track systems. We offer easy to install single or two circuit tracks, connectors, power feeds, monopoint canopies, mounting accessories, and a variety of other track lighting accessories. Our high quality accessories are suitable for use in residential, commercial and retail applications.

Single & Two Circuit Tracks



Single Circuit Track

Elco Single Circuit Track is UL/CUL listed, 120V, 20 amp circuit and is solid, safe and easy to use, with quality recognized throughout the lighting industry. For use in residential, commercial and retail applications.



Two Circuit Track

ELCO Two Circuit Track is UL/CUL listed, 120V, 20 amps per circuit and provides greater system flexibility. The ELCO two circuit track system allows each 20 amp circuit to be independently switched. Provides maximum flexibility, with a low profile. Suitable for a wide range of commercial, merchandising and residential applications.

Connectors

Connectors push easily into the ends of the track, eliminating splicing. Polarity arrows on connectors assure proper electrical installation. Just align arrows with polarity line on track and push in. L's, T's, X's and Flexible Connector allow track to be assembled in almost any pattern.

Grounding

To ensure safe operation the entire track system is fully polarized and grounded. Grounding is accomplished automatically by a separate solid copper ground conductor in the track. The ground conductor maintains continuity to the building's grounding system through the ground contact fingers in each of the connectors.

Installation of Track Head

Most Elco track head can be use on single and two circuit track systems. The track head has a stem, with three blades. Two rigid blades on one side, and a single adjustable blade on the other. The single blade can move up or down until it locks into position for the circuit #1 (close to lamp) or circuit #2 (away from lamp).


Polarity

The visual polarity groove on the top of the single and two circuit track indicates the neutral/ground side of the track. For proper fixture installation, insert the lamp holder into the track and turn (twist) the two-blade side of the lamp holder towards (into) the polarity side of the track.

Single Circuit Track and Accessories

Single Circuit Track

Track supplied with dead end and mounting hardware.





White		Black	
EP002W	2'	EP002B	2'
EP004W	4'	EP004B	4'
EP006W	6'	EP006B	6'
EP008W	8'	EP008B	8'
EP012W	12'	EP012B	12'
Bronze		Nickel	
EP002BZ	2'	EP002N	2'
EP004BZ	4'	EP004N	4'
EP006BZ	6'	EP006N	6'
EP008BZ	8'	EP008N	8'



Live End Connector

Live end connector use for direct wiring.


EP801W	White
EP801B	Black
EP801BZ	Bronze
EP801N	Nickel



Flexible Connector

Flexible connector to join two track sections at an angle up to 90°. Can be used as a feed point.


EP802W	White
EP802B	Black
EP802BZ	Bronze
EP802N	Nickel



Straight Connector

Power feedable connector to join two track sections.


EP803W	White
EP803B	Black
EP803BZ	Bronze
EP803N	Nickel



L Connector

Power feedable connector to join two track sections at a 90° angle.



EP804W	White
EP804B	Black
EP804BZ	Bronze
EP804N	Nickel



T Connector

Power feedable connector to join three track sections.


EP805W	White
EP805B	Black
EP805BZ	Bronze
EP805N	Nickel



X Connector

Power feedable connector to join four track sections.


EP806W	White
EP806B	Black
EP806BZ	Bronze
EP806N	Nickel



Mini Connector

Mini Connector to join two track sections. Cannot be used as a feed point.


EP808W	White
EP808B	Black
EP808BZ	Bronze
EP808N	Nickel




Floating Canopy

Can be used anywhere along length of track to supply power. Includes end cap.

EP809W	White
EP809B	Black
EP809BZ	Bronze
EP809N	Nickel




Single Circuit Track Accessories



End Feed Kit

Kit includes live end feed and canopy to mount on outlet box. 4 1/2" x 4 1/2" x 1/4" thick.


- EP810W** White
- EP810B** Black
- EP810BZ** Bronze
- EP810N** Nickel



Dead End

Dead end cap for single and two circuit track.


- EP812W** White
- EP812B** Black
- EP812BZ** Bronze
- EP812N** Nickel



T-Bar Ceiling Feed

Live feed with outlet box for use with T-bar ceilings.


- EP817W** White
- EP817B** Black
- EP817BZ** Bronze
- EP817N** Nickel



Dead Mini Connector

Dead Mini Connector to join two track sections without passing the power.


- EP825W** White
- EP825B** Black
- EP825BZ** Bronze
- EP825N** Nickel



T-Bar Ceiling Feed

In-line T-bar ceiling feed.


- EP827W** White
- EP827B** Black



Cord and Plug Connector

Cord and Plug Connector for single circuit track. 10 Amp MAX. or 1200W. 12 ft. long.


- EP850W** White
- EP850B** Black
- EP850BZ** Bronze
- EP850N** Nickel



Conduit Connector

To start a surface run.

- EP880W** White
- EP880B** Black
- EP880BZ** Bronze
- EP880N** Nickel




Conduit Continuation Kit

Kit includes: (1) Left and (1) Right feed, to continue around obstructions with 1/2" surface conduit.

- EP979W** White
- EP979B** Black

Single Circuit Track Accessories



Live Feed with Current Limiter

Current Limiter for single circuit track. 1A to 12A available.

White


EP840W-1A	1 Amp
EP840W-2A	2.5 Amp
EP840W-3A	3 Amp
EP840W-4A	4 Amp
EP840W-5A	5 Amp
EP840W-7A	7.5 Amp
EP840W-10A	10 Amp
EP840W-12A	12 Amp

Black

EP840B-1A	1 Amp
EP840B-2A	2.5 Amp
EP840B-3A	3 Amp
EP840B-4A	4 Amp
EP840B-5A	5 Amp
EP840B-7A	7.5 Amp
EP840B-10A	10 Amp
EP840B-12A	12 Amp

Bronze

EP840BZ-1A	1 Amp
EP840BZ-2A	2.5 Amp
EP840BZ-3A	3 Amp
EP840BZ-4A	4 Amp
EP840BZ-5A	5 Amp
EP840BZ-7A	7.5 Amp
EP840BZ-10A	10 Amp
EP840BZ-12A	12 Amp



In-Line Feed Connector with Current Limiter

Current Limiter for single circuit track. 1A to 12A available.

White

EP841W-1A	1 Amp
EP841W-2A	2.5 Amp
EP841W-3A	3 Amp
EP841W-4A	4 Amp
EP841W-5A	5 Amp
EP841W-7A	7.5 Amp
EP841W-10A	10 Amp
EP841W-12A	12 Amp


Black

EP841B-1A	1 Amp
EP841B-2A	2.5 Amp
EP841B-3A	3 Amp
EP841B-4A	4 Amp
EP841B-5A	5 Amp
EP841B-7A	7.5 Amp
EP841B-10A	10 Amp
EP841B-12A	12 Amp

Two Circuit Track and Accessories

Two Circuit Track

Track supplied with dead end and mounting hardware.




White
EC002W 2'
EC004W 4'
EC006W 6'
EC008W 8'




Black
EC002B 2'
EC004B 4'
EC006B 6'
EC008B 8'

Straight Connector

Power feedable connector to join two track sections.




EC803W White
EC803B Black



T Connector

Power feedable connector to join three track sections.


EC805W White
EC805B Black



Mini Connector

Mini Connector to join two track sections. Cannot be used as a feed point


EC808W White
EC808B Black



Live End Connector

Two Circuit live end connector to start a run.


EC801W White
EC801B Black



Flexible Connector

Power feedable connector to join two track sections up to 90° angle.



EC802W White
EC802B Black



L Connector

Power feedable connector to join two track sections at a 90° angle.


EC804W White
EC804B Black



X Connector

Power feedable connector to join four track sections.

EC806W White
EC806B Black




Floating Canopy

Can be used anywhere along length of track to supply power. Includes end cap.

EC809W White
EC809B Black


Two Circuit Track Accessories



Dead End

Dead End Cap for single and two circuit track.



- EC812W** White
- EC812B** Black



T-Bar Ceiling Feed

Live feed with outlet box for use with T-bar ceilings.


- EC817W** White
- EC817B** Black



Conduit Connector

To start a surface run.

- EC880W** White
- EC880B** Black



Two Circuit Live-End Feed Connector with Current Limiter


1A to 12A available. Separate circuit breaker for each circuit. Custom current rating available upon request.

- EC840W** White
- EC840B** Black

Product Number Builder

ELCO 2 Circuit Live-End Feed	Finish	Circuit 1	Circuit 2
EC840			
	W White	1A 1 Amp	1A 1 Amp
	B Black	2A 2.5 Amp	2A 2.5 Amp
		3A 3 Amp	3A 3 Amp
		4A 4 Amp	4A 4 Amp
		5A 5 Amp	5A 5 Amp
		7A 7.5 Amp	7A 7.5 Amp
		10A 10 Amp	10A 10 Amp
		12A 12.5 Amp	12A 12.5 Amp

Example: **EC840W1A7A** [ELCO 2 Circuit Live-End Feed, White, 1 Amp, 7 Amp]



Two Circuit In-Line Feed Connector with Current Limiter

1A to 12A available. Separate circuit breaker for each circuit. Custom current rating available upon request.


- EC841W** White
- EC841B** Black

Product Number Builder

ELCO 2 Circuit In-Line Feed	Finish	Circuit 1	Circuit 2
EC841			
	W White	1A 1 Amp	1A 1 Amp
	B Black	2A 2.5 Amp	2A 2.5 Amp
		3A 3 Amp	3A 3 Amp
		4A 4 Amp	4A 4 Amp
		5A 5 Amp	5A 5 Amp
		7A 7.5 Amp	7A 7.5 Amp
		10A 10 Amp	10A 10 Amp
		12A 12.5 Amp	12A 12.5 Amp

Example: **EC841B2A12A** [ELCO 2 Circuit In-Line Feed, Black, 2.5 Amp, 12.5 Amp]

General Track Accessories



Louvers

Louver for ET630 for PAR30.

- EP222W** White
- EP222B** Black

Louver for ET631 and ET633 for PAR30.

- EP333W** White
- EP333B** Black

Louver for ET640 and ET650 for PAR38.


- EP444W** White
- EP444B** Black



Snoot

1½" Snoot to reduce glare and spill light. For use with ET526, ET527, ET531, and ET535.

- EP300W** White
- EP300B** Black



Barndoors

Barndoors for ET640 and ET650 for PAR38 or R40 with holder ring.


- EP422W** White
- EP422B** Black



Track Adapter Trim

For use with standard 6" recessed housings. Allow track lamp holders to be use with recessed intallations. Up to 150W MAX. 7½" O.D.

- EP577W** White
- EP577B** Black



Outlet Box Cover

Outlet box cover. Screws not included. 5" x 5" x ¼" x 1¼" Sq.

- EP800W** White
- EP800B** Black
- EP800BZ** Bronze



Monopoint Canopy

Allows any lamp holder (300W MAX.) to be converted to canopy installation. For Line Voltage fixtures.


- EP811W** White
- EP811B** Black
- EP811BZ** Bronze
- EP811N** Nickel



Sign Hanger

Sign Hanger with hook for single and two circuit track. Holds up to 25 lbs.

- EP813W** White
- EP813B** Black
- EP813BZ** Bronze
- EP813N** Nickel



Outlet Adapter

Outlet Adapter for single and two circuit track.

- EP814W** White
- EP814B** Black
- EP814BZ** Bronze
- EP814N** Nickel



Pendant Adapter

For single and two circuit track with strain relief connector for cord or chain hung fixtures. Holds up to 25 lbs.

- EP815W** White
- EP815B** Black
- EP815BZ** Bronze
- EP815N** Nickel

General Track Accessories



Canopy Adapter

For Low Voltage fixtures with transformer. Can be used with EP900.

- EP816W** White
- EP816B** Black
- EP816BZ** Bronze
- EP816N** Nickel



Round Monopoint Canopy

For Line Voltage fixtures. 4 5/8" O.D.

- EP819W** White
- EP819B** Black
- EP819BZ** Bronze



Bardoors

For use with ET547.


- EP820W** White
- EP820B** Black

For use with ET631, ET635, ET637, ET639, and ET644.

- EP822W** White
- EP822B** Black

For use with ET630.


- EP823W** White
- EP823B** Black



Straight Channel

Provides support for straight connection points in suspended track system. Track sits inside the channel. 16 1/4" long.


- EP844W** White
- EP844B** Black



L Channel

Support corner connection points in suspended track system. Track sits inside the channel. 16 1/4" long in each side.


- EP845W** White
- EP845B** Black



Dimmer Switch

Dimmer with ON/OFF switch. For Line Voltage fixtures. 150W MAX

- EP901W** White
- EP901B** Black



Clamp Cord and Plug

Clamp with 6 ft. cord and plug with female track connector for attaching a Line Voltage fixture.

- EP903W** White
- EP903B** Black



48" Steel Stem

For additional pendant length. Includes coupling. Use with EP918, EP924, EP936, and EP948.

- EP904W** White
- EP904B** Black




T-Bar Attachment Clip

Allows track to be attached to inverted T-Bar ceiling. Order as follow: (2) clips for 2' or 4' track, (3) clips for 6' track, (4) clips for 8' or 12' track.

- EP989B**

General Track Accessories



Slope Ceiling Fixture Adapter

Allows use of extension wands on slope ceiling. 0°-90°.


EP906W White
EP906B Black



Track Pendant Kit

Track pendant kit with 60" stainless steel cable. 1/16" stranded.

EP960W White
EP960B Black



Clamp Cord and Track Adapter

Connects to Line Voltage track. Includes female track connector for attaching a Line Voltage fixture.

EP907W White
EP907B Black



Pendant Assembly

Suspends track from ceiling. Order as follow: (2) kits for 2' or 4' track, (3) kits for 6' track, (4) kits for 8' track, (5) kits for 12', (1) EP807 per feed.


White		Black	
EP918W	18"	EP918B	18"
EP924W	24"	EP924B	24"
EP936W	36"	EP936B	36"
EP948W	48"	EP948B	48"



Sloped Ceiling Pendant Adapter

Sloped Ceiling Pendant adapter for use with EP918, EP924, EP936, and EP948.


EP905W White
EP905B Black



Wire Cover

Wire cover for power feed through with pendant assembly. One per run. For use with EP918 to EP948.

EP807W White
EP807B Black
EP807BZ Bronze
EP807N Nickel



Extension Wand

Line voltage extension wands. Drops head from track.

White		Black	
EP881W	6"	EP881B	6"
EP882W	12"	EP882B	12"
EP818W	18"	EP818B	18"
EP824W	24"	EP824B	24"
EP836W	36"	EP836B	36"
EP848W	48"	EP848B	48"



Pendant Lighting

Add a pop of color to your kitchen island with a series of our sleek and stylish glass pendants. Modern and traditional shapes combined with popular colors makes our glass pendants the perfect addition to any home design. Available in LED, Line and Low Voltage, our energy efficient pendants are designed to save you money, maintenance and energy.

LED Die-Cast Aluminum Pendants

Sleek and modern die-cast aluminum pendants

LED Die-Cast Aluminum Pendants include a Flat Canopy



White
EDL8030W
700 lm
3000K
10W

Black
EDL8030B
700 lm
3000K
10W

White
EDL8040W
750 lm
4000K
10W


Black
EDL8040B
750 lm
4000K
10W

LED Bait™ (2" x 8")



- Modern Die-cast Aluminum Pendant
- Canopy included
- ETL listed
- 50,000 hours life-span
- Optional beam angle lens: EP719C (15°) or EP720C (25°)

Input Power	10W
Lumens	700 - 750
Color Temp.	3000K - 4000K
Input Volt	120V
Dimmable	Yes
Beam Angle	38°



White
EDL8130W
1490 lm
3000K
18W

Black
EDL8130B
1490 lm
3000K
18W

White
EDL8140W
1610 lm
4000K
18W


Black
EDL8140B
1610 lm
4000K
18W

LED Bait™ (3" x 8")



- Modern Die-cast Aluminum Pendant
- Canopy included
- ETL listed
- 50,000 hours life-span
- Optional beam angle lens: EP722C (15°) or EP723C (25°)

Input Power	18W
Lumens	1490 - 1610
Color Temp.	3000K - 4000K
Input Volt	120V
Dimmable	Yes
Beam Angle	38°



Optional Steel Stems for LED Die-Cast Aluminum Pendants

EP883W White
EP883B Black

EP884W White
EP884B Black

EP885W White
EP885B Black

• 24" L x 3/8" O.D.

• 48" L x 3/8" O.D.

• 72" L x 3/8" O.D.

LED Die-Cast Aluminum Pendants

Sleek and modern die-cast aluminum pendants

LED Die-Cast Aluminum Pendants include a Flat Canopy



White
EDL8230W
1920 lm
3000K
30W

Black
EDL8230B
1920 lm
3000K
30W

White
EDL8240W
2070 lm
4000K
30W


Black
EDL8240B
2070 lm
4000K
30W

LED Bait™ (3" x 10")



- Modern Die-cast Aluminum Pendant
- Canopy included
- ETL listed
- 50,000 hours life-span
- Optional beam angle lens: EP722C (15°) or EP723C (25°)

Input Power	30W
Lumens	1920 - 2070
Color Temp.	3000K - 4000K
Input Volt	120V
Dimmable	Yes
Beam Angle	38°



White
EDL8330W
2690 lm
3000K
40W

Black
EDL8330B
2690 lm
3000K
40W

White
EDL8340W
2900 lm
4000K
40W


Black
EDL8340B
2900 lm
4000K
40W

LED Bait™ (4" x 10")



- Modern Die-cast Aluminum Pendant
- Canopy included
- ETL listed
- 50,000 hours life-span

Input Power	40W
Lumens	2690 - 2900
Color Temp.	3000K - 4000K
Input Volt	120V
Dimmable	Yes
Beam Angle	38°



Optional Steel Stems for LED Die-Cast Aluminum Pendants

EP883W White
EP883B Black

EP884W White
EP884B Black

EP885W White
EP885B Black

- 24" L x 3/8" O.D.

- 48" L x 3/8" O.D.

- 72" L x 3/8" O.D.

LED Glass Pendants


Add a pop of color to any room space with our modern and stylish glass pendants



LED Bale™

- Modern LED Glass Pendant
- ETL Listed
- 50,000 hours life-span
- 6 ½" ft. metal finish cable


Input Power	5W
Lumens	300
Color Temp.	3000K
Input Volt	120V
Dimmable	Yes



LED Blake™

- Modern LED Glass Pendant
- ETL Listed
- 50,000 hours life-span
- 6 ½" ft. metal finish cable

Input Power	5W
Lumens	300
Color Temp.	3000K
Input Volt	120V
Dimmable	Yes



LED Glass Pendants

Add a pop of color to any room space with our modern and stylish glass pendants



LED Glass Pendants include a Flat Canopy with 5W LED Driver



LED Becket™

- Modern LED Glass Pendant
- ETL Listed
- 50,000 hours life-span
- 6 ½" ft. metal finish cable


Input Power	5W
Lumens	300
Color Temp.	3000K
Input Volt	120V
Dimmable	Yes



LED Barrel™

- Modern LED Glass Pendant
- ETL Listed
- 50,000 hours life-span
- 6 ½" ft. metal finish cable

Input Power	5W
Lumens	300
Color Temp.	3000K
Input Volt	120V
Dimmable	Yes




Line Voltage Glass Pendants

Combine with Line Voltage Monopoint Canopy or Track Connector




Line Voltage Bale™

- E12 Socket for 60W MAX. Candelabra Lamp
- Combine with ECT or ETT Line Voltage connectors
- 6 ½ ft. clear finish cord




Line Voltage Blake™

- E26 Medium Base Socket for 60W A19 Lamp
- Combine with ECT or ETT Line Voltage connectors
- 6 ½ ft. clear finish cord



Line Voltage Becket™

- E26 Medium Base Socket for 60W A19 Lamp
- Combine with ECT or ETT Line Voltage connectors
- 6 ½ ft. clear finish cord




Line Voltage Glass Pendants

Combine with Line Voltage Monopoint Canopy or Track Connector



Line Voltage Barrel™

- E12 Socket for 60W MAX. Candelabra Lamp
- Combine with ECT or ETT Line Voltage connectors
- 6 ½ ft. clear finish cord



Line Voltage Glass Pendants **Accessories**



Monopoint Canopy

ECTW White
ECTB Black
ECTN Nickel

- 5/8" H x 5" O.D.



Track Connector

ETTW White
ETTB Black
ETTN Nickel

- For 1 or 2 Circuit Tracks

Low Voltage Glass Pendants


Combine with Low Voltage Track Connectors



Athena E20AT Cobalt E20CO Frost E20FR Mars E20MA Autumn E20AU

Low Voltage Bale™


- GU5.3 Base Socket for 50W MAX. MR16 or JC Lamp
- Combine with ELW, ETV, ECL, ECF, or EP2015 Low Voltage connectors
- 6 ½ ft. clear finish cord



Athena E21AT Cobalt E21CO Frost E21FR Mars E21MA Autumn E21AU

Low Voltage Blake™


- GU5.3 Base Socket for 50W MAX. MR16 or JC Lamp
- Combine with ELW, ETV, ECL, ECF, or EP2015 Low Voltage connectors
- 6 ½ ft. clear finish cord



Athena E22AT Cobalt E22CO Frost E22FR Mars E22MA Autumn E22AU

Low Voltage Becket™

- GU5.3 Base Socket for 50W MAX. MR16 or JC Lamp
- Combine with ELW, ETV, ECL, ECF, or EP2015 Low Voltage connectors
- 6 ½ ft. clear finish cord



Low Voltage Glass Pendants

Combine with Line Voltage Monopoint Canopy or Track Connector



Athena
E23AT

Cobalt
E23CO


Frost
E23FR

Mars
E23MA

Autumn
E23AU

Low Voltage Barrel™

- GU5.3 Base Socket for 50W MAX. MR16 or JC Lamp
- Combine with ELW, ETV, ECL, ECF, or EP2015 Low Voltage connectors
- 6 ½ ft. clear finish cord



Low Voltage Glass Pendants **Accessories**



50W Track Transformer

ELWW White
ELWB Black
ELWN Nickel

- For Low Voltage Pendants



50W Vertical Track Transformer

ETVW White
ETVB Black
ETVN Nickel

- For 1 or 2 Circuit Tracks



50W Semicircular Canopy with Transformer

ECLW White
ECLB Black
ECLN Nickel

- For Low Voltage Pendants



50W Flat Canopy with Transformer

ECFW White
ECFB Black
ECFN Nickel

- For Low Voltage Pendants



Mini Track Adapter

EP2015W White
EP2015B Black

- For Low Voltage Pendants

Low Voltage Decorative Pendants


Decorative Light Pendants to match any room design



Satin Nickel Pendant (Ceiling Mount)

EDL30


- 12V 50W MR16 Lamp
- Satin Nickel Canopy for ceiling mount
- Electronic Transformer
- Matching 60" cord included



Satin Nickel Pendant

EDL31


- 12V 50W MR16 Lamp
- Track adapter included
- Electronic Transformer
- Matching 60" cord included




Red Glass Sconce Pendant

- 120V 50W JC Lamp
- Canopy for ceiling mount
- 60" cord included
- 120V 50W JC Lamp
- Track adapter included
- 60" cord included
- 12V 50W MR16 Lamp
- Track adapter included
- Transformer and 60" cord included


EDL70R Black Cord
EDL71R White Cord



EDL72R Black Cord
EDL73R White Cord



EDL74R Black Cord
EDL75R White Cord



Dimmer Compatibility Chart

ET612D, ET613D, ET614D, ET615D, ET616D, ET617, ET61830D, ET61930D, ET62030D, ET62130D, ET62230D, ET62330D, ET62430D, ET62530D, ET62630D, ET62730D, ET62830D, ETW4230, ETW4330 & ETW4430

Manufacturer	Product	Part Number	Dimmed Light Output Range
Triac/ELV Type Dimmers			
Lutron	Ariadni® 150W Single Pole/3-Way Dimmer	AYCL-153P	10% - 100%
	Ariadni® 250W Single Pole/3-Way Dimmer	AYCL-253P	10% - 100%
	Skylark Contour® 150W Single Pole/3-Way Dimmer	CTCL-153P	10% - 100%
	Diva® 150W Single Pole/3-Way Dimmer	DVCL-153P	10% - 100%
	Diva® 250W Single Pole/3-Way Dimmer	DVCL-253P	10% - 100%
	Diva® 450W 3-Way Magnetic Low Voltage Dimmer	DVLV-603P	10% - 100%
	Diva® 150W Single Pole/3-Way Dimmer	DVSCCL-153P	10% - 100%
	Diva® 250W Single Pole/3-Way Dimmer	DVSCCL-253P	10% - 100%
	Diva® 150W Single Pole/3-Way Dimmer	DVWCL-153PH-WH	10% - 100%
	Grafik T® 150W Single Pole Dimmer	GT-150	10% - 100%
	Grafik T® 250W Single Pole/Multi-Location Dimmer	GTJ-250M	10% - 100%
	Maestro® 150W Single Pole/3-Way/Multi-Location Dimmer	MACL-153MH-WH	10% - 100%
	Skylark® 150W Single Pole/3-Way Dimmer	SCL-153P	10% - 100%
	Skylark® 300W Single Pole Electronic Low Voltage Dimmer	SELV-300P	10% - 100%
Toggler® 150W Single Pole/3-Way Dimmer	TGCL-153P	10% - 100%	

ET743D, ET744D, ET745D, ET746D, ETW4030, ETW4040, ETW4130 & ETW4140

Manufacturer	Product	Part Number	Dimmed Light Output Range
Cooper	DEVINE Decorator Single Pole/3-Way Preset Dimmer	DLC03P	10% - 100%
	SKYE Slide Single Pole/3-Way Preset Dimmer	SLC03P	10% - 100%
	AL Series Decorator Single Pole/3-Way Preset Dimmer	DAL06P	10% - 100%
Lightolier	Sunrise 3-Way Preset Electronic Low Voltage Dimmer	ZP260QEW	8% - 100%
Lutron	Skylark® Contour Single Pole/3-Way Dimmer	CT-103P	8% - 100%
	Diva® Single Pole Incandescent/Halogen Preset Dimmer	DV-600P	10% - 100%
	Diva® C-L Single Pole/3-Way Dimmer	DVCL-153P	7% - 100%
	Diva® 3-Way Electronic Low Voltage Dimmer	DVELV-303P	8% - 100%
	Lumea® Single Pole Incandescent/Halogen Preset Dimmer	LG-600P	10% - 100%
Maestro® Single Pole/Multi-Location Electronic Low Voltage Dimmer	MAELV-600	8% - 100%	

Dimmer Compatibility Chart

ET743D, ET744D, ET745D, ET746D, ETW4030, ETW4040, ETW4130 & ETW4140

Manufacturer	Product	Part Number	Dimmed Light Output Range
Lutron	Skylark® Single Pole Incandescent/Halogen Slide to Off Dimmer	S-600P	10% - 100%
	Skylark® Single Pole/3-Way Incandescent/Halogen Preset "Eco-Dim" Dimmer	S-603PG	5% - 85%
	Skylark® Single Pole Electronic Low Voltage Preset Dimmer	SELV-300P	8% - 100%
	Toggler® Single Pole Incandescent Dimmer	TG-600P	10% - 100%
	Toggler® C-L Single Pole/3-Way Dimmer	TGCL-153P	7% - 100%
	Faetra® Single Location Digital Fade Dimmer	FAELV-500	8% - 100%
Leviton	Decora 4-Level Step Electro-Mechanical Incandescent Dimmer	6161	10% - 100%
	SureSlide Electro-Mechanical Incandescent Dimmer	6631-2	10% - 100%
	SureSlide 3-Way Preset Incandescent Dimmer	6633-P	10% - 100%
	Trimatron Deluxe 3-Way Push On/Off Rotary Incandescent Dimmer	6683-IW	10% - 100%
	IllumaTech Single Pole/3-Way Electronic Low Voltage Dimmer	IPE04	8% - 100%
	IllumaTech Single Pole/3-Way Incandescent Dimmer	IPI06-1LZ	10% - 100%
	Vizia Single Pole/3-Way Electronic Low Voltage Dimmer	VPE06	8% - 100%

ET750D & ET752D

Manufacturer	Product	Part Number	Dimmed Light Output Range
Cooper	ASPIRE Decorator Single Pole/3-Way Dimmer	9573WS	10% - 100%
	DEVINE Decorator Dimmer	DI06P-A-K	10% - 100%
Legrand	Adorne® Paddle 450W Single Pole/3-Way Dimmer	ADPD453L-W2	10% - 100%
Leviton	IllumaTech Single Pole/3-Way Incandescent Dimmer	IPI06	10% - 100%
	Decora Sureslide Single Pole Slide-to-Off Incandescent Dimmer	6631-LW	10% - 100%
	Decora Sureslide Single Pole/3-Way Magnetic Low Voltage Dimmer	6613-PL	8% - 100%
Lutron	Ariadni Single Pole/3-Way Dimmer	AY-600P-AL	10% - 100%
	Diva® C-L Single Pole/3-Way Dimmer	DVCL-153PR	7% - 100%
	Diva® Single Pole Incandescent/Halogen Dimmer	DV-600P-WH	10% - 100%
	Glyder® Single Pole Magnetic Low Voltage Dimmer	GLV-600-WH	8% - 100%
	Maestro® Incandescent/Halogen Digital Fade Dimmer	MRF2-600M-WH	10% - 100%
	Nova® Single Pole Incandescent/Halogen Slide-to-Off Dimmer	N-600	10% - 100%
	Skylark® Single Pole/3-Way Incandescent/Halogen "Eco-Dim" Dimmer	S-603PG	5% - 85%
	Skylark® Single Pole/3-Way Incandescent/Halogen Dimmer	S-600P-AL	10% - 100%
Skylark® Single Pole Magnetic Low Voltage Dimmer	SLV-600-WH	8% - 100%	

Dimmer Compatibility Chart

ET756

Manufacturer	Product	Part Number	Dimmed Light Output Range
Cooper	ASPIRE Single Pole/3-Way Dimmer	9530	10% - 100%
Lightolier	Momentum Preset Single Pole/Multi-Location Incandescent Dimmer	MP600	10% - 100%
Philips	Sunrise Single Pole/3-Way Dimmer	SR150LED120	10% - 100%
Lutron	Skylark® Single Pole Magnetic Low Voltage Preset Dimmer	SLV-600	8% - 100%
	Skylark® Single Pole Incandescent/Halogen Dimmer	S2-L	10% - 100%
	Glyder® Single Pole Incandescent/Halogen Slide-to-Off Dimmer	GL-600H	10% - 100%
	Nova® Single Pole 2-Wire Fluorescent Slide-to-Off Dimmer	NFTU-5A	10% - 100%
	Diva® Single Pole Magnetic Low Voltage Dimmer	DVLV-600P	8% - 100%
Leviton	Trimatron Deluxe Single Pole Rotary On/Off Electro-Mechanical Incandescent Dimmer	6602	10% - 100%
	Trimaatron Deluxe Single Pole Rotary Push On/Off Electro-Mechanical Incandescent Dimmer	6681	10% - 100%
	Trimatron Deluxe 3-Way Illuminated Rotary Pus On/Off Electro-Mechanical Incandescent Dimmer	6684	10% - 100%
	Rotary Single Pole Dimmer	700	10% - 100%
	Rotary Single Pole Push On/Off Dimmer	705	10% - 100%
	Decora SureSlide 3-Way Preset Incandescent Dimmer	6633	10% - 100%
	Decora SureSlide Single Pole/3-Way Preset Dimmer	6674	10% - 100%
	IllumaTech Single Pole/3-Way Preset Dimmer	IPI06-1LZ	10% - 100%

For Reference Only: Testing conducted by ELCO Lighting is not a substitute for and does not imply certification by an independent laboratory or any other standards certification. Refer to manufacturer specifications for more detailed information on product certifications and standards. Consult the dimmer manufacturer prior to installation to ensure compatibility.

*NOTE: Refer to dimmer manufacturer's documentation for installation instructions and circuit details


Disclaimer: Minimum and maximum loads for LEDs and CFLs are given in number of lamps and may vary depending on the lamp being used.

Photometric Report

LED Track Fixtures

PHOTOMETRIC REPORT

Product #: ET612D
 Wattage/Lumens: 10W / 701 lm
 Luminaire LPW: 70 lm / W



CANDLE POWER SUMMARY

Degrees Vertical	0°
0	1460
5	322
15	892
25	382
35	120
45	37
55	14
65	4
75	1
85	0
90	0

ILLUMINANCE AT A DISTANCE


Distance to Target Plane	Footcandles Beam Center	Beam Diameter
4'	91.2	2.6'
6'	40.6	4.0'
8'	22.8	5.3'
10'	14.6	6.6'

ZONAL LUMEN SUMMARY

Zone	Lumens	%Luminaire
0-30°	557.07	79.50
0-40°	647.19	92.40
0-60°	695.87	99.30
0-90°	700.67	100.00

PHOTOMETRIC REPORT

Product #: ET740
 Wattage/Lumens: 10W / 603 lm
 Luminaire LPW: 60 lm / W



CANDLE POWER SUMMARY

Degrees Vertical	0°
0	2054
5	2003
15	973
25	403
35	141
45	10
55	6
65	5
75	3
85	1
90	0

ILLUMINANCE AT A DISTANCE


Distance to Target Plane	Footcandles Beam Center	Beam Diameter
4'	128	1.7'
6'	57.0	2.6'
8'	32.1	3.5'
10'	20.5	4.4'

ZONAL LUMEN SUMMARY

Zone	Lumens	%Luminaire
0-30°	526.75	87.30
0-40°	585.07	97.00
0-60°	596.91	98.90
0-90°	603.27	100.00

PHOTOMETRIC REPORT

Product #: ET741
 Wattage/Lumens: 10W / 581 lm
 Luminaire LPW: 58 lm / W



CANDLE POWER SUMMARY

Degrees Vertical	0°
0	1131
5	1119
15	908
25	459
35	143
45	12
55	7
65	3
75	2
85	1
90	0

ILLUMINANCE AT A DISTANCE

Distance to Target Plane	Footcandles Beam Center	Beam Diameter
4'	70.7	3.0'
6'	31.4	4.6'
8'	17.7	6.1'
10'	11.3	7.6'

ZONAL LUMEN SUMMARY


Zone	Lumens	%Luminaire
0-30°	501.47	86.30
0-40°	563.07	96.90
0-60°	576.81	99.20
0-90°	581.26	100.00

Photometrics

LED Track Fixtures

PHOTOMETRIC REPORT

Product #: ET742
 Wattage/Lumens: 10.1 W / 600 lm
 Luminaire LPW: 59 lm / W



CANDLE POWER SUMMARY

Degrees Vertical	0°
0	869
5	868
15	753
25	532
35	219
45	17
55	7
65	4
75	2
85	1
90	0

ILLUMINANCE AT A DISTANCE


Distance to Target Plane	Footcandles Beam Center	Beam Diameter
4'	54.3	3.9'
6'	24.1	5.9'
8'	13.6	7.8'
10'	8.69	9.8'

ZONAL LUMEN SUMMARY

Zone	Lumens	%Luminaire
0-30°	482.06	80.30
0-40°	577.17	96.10
0-60°	595.20	99.10
0-90°	600.42	100.00

PHOTOMETRIC REPORT

Product #: ET743D
 Wattage/Lumens: 15.6 W / 937 lm
 Luminaire LPW: 60 lm / W



CANDLE POWER SUMMARY

Degrees Vertical	0°
0	3401
5	2494
15	673
25	423
35	321
45	86
55	12
65	8
75	6
85	2
90	1

ILLUMINANCE AT A DISTANCE


Distance to Target Plane	Footcandles Beam Center	Beam Diameter
4'	213	1.2'
6'	94.5	1.9'
8'	53.1	2.5'
10'	34.0	3.1'

ZONAL LUMEN SUMMARY

Zone	Lumens	%Luminaire
0-30°	632.58	67.50
0-40°	829.31	88.50
0-60°	922.34	98.40
0-90°	937.05	100.00

PHOTOMETRIC REPORT

Product #: ET744D
 Wattage/Lumens: 15.6 W / 940 lm
 Luminaire LPW: 60 lm / W



CANDLE POWER SUMMARY

Degrees Vertical	0°
0	2306
5	1983
15	794
25	423
35	319
45	94
55	14
65	8
75	7
85	2
90	1

ILLUMINANCE AT A DISTANCE

Distance to Target Plane	Footcandles Beam Center	Beam Diameter
4'	144	1.8'
6'	64.0	2.7'
8'	36.0	3.6'
10'	23.1	4.4'

ZONAL LUMEN SUMMARY


Zone	Lumens	%Luminaire
0-30°	631.98	67.30
0-40°	828.41	88.20
0-60°	925.26	98.50
0-90°	939.69	100.00

Photometrics

LED Track Fixtures

PHOTOMETRIC REPORT

Product #: ET745D
 Wattage/Lumens: 15.6 W / 936 lm
 Luminaire LPW: 60 lm / W



CANDLE POWER SUMMARY

Degrees Vertical	0°
0	1524
5	1410
15	936
25	461
35	318
45	90
55	17
65	9
75	7
85	1
90	1

ILLUMINANCE AT A DISTANCE


Distance to Target Plane	Footcandles Beam Center	Beam Diameter
4'	95.3	2.7'
6'	42.3	4.1'
8'	23.8	5.5'
10'	15.2	6.8'

ZONAL LUMEN SUMMARY

Zone	Lumens	%Luminaire
0-30°	618.60	66.10
0-40°	816.87	87.30
0-60°	917.51	98.00
0-90°	936.11	100.00

PHOTOMETRIC REPORT

Product #: ET746D
 Wattage/Lumens: 14.8 W / 949 lm
 Luminaire LPW: 64 lm / W



CANDLE POWER SUMMARY

Degrees Vertical	0°
0	1000
5	995
15	845
25	632
35	441
45	204
55	23
65	14
75	9
85	4
90	1

ILLUMINANCE AT A DISTANCE


Distance to Target Plane	Footcandles Beam Center	Beam Diameter
4'	62.5	4.4'
6'	24.8	6.6'
8'	15.6	8.8'
10'	10.0	11.0'

ZONAL LUMEN SUMMARY

Zone	Lumens	%Luminaire
0-30°	572.21	60.30
0-40°	811.68	85.50
0-60°	926.81	97.70
0-90°	949.10	100.00

PHOTOMETRIC REPORT

Product #: ET750D
 Wattage/Lumens: 13.4 W / 1135 lm
 Luminaire LPW: 85 lm / W



CANDLE POWER SUMMARY

Degrees Vertical	0°
0	3094
5	2768
15	1417
25	562
35	194
45	63
55	26
65	6
75	1
85	1
90	1

ILLUMINANCE AT A DISTANCE

Distance to Target Plane	Footcandles Beam Center	Beam Diameter
4'	193	1.9'
6'	85.9	2.9'
8'	48.3	3.9'
10'	30.9	4.9'

ZONAL LUMEN SUMMARY


Zone	Lumens	%Luminaire
0-30°	898.68	79.20
0-40°	1042.61	91.80
0-60°	1127.19	99.30
0-90°	1135.27	100.00

Photometrics

LED Track Fixtures

PHOTOMETRIC REPORT

Product #: ET752D
Wattage/Lumens: 13.4 W / 1127 lm
Luminaire LPW: 84 lm / W



CANDLE POWER SUMMARY

Degrees Vertical	0°
0	2349
5	2127
15	1436
25	615
35	194
45	60
55	22
65	6
75	1
85	1
90	1

ILLUMINANCE AT A DISTANCE


Distance to Target Plane	Footcandles Beam Center	Beam Diameter
4'	147	2.6'
6'	65.2	4.0'
8'	36.7	5.3'
10'	23.5	6.6'

ZONAL LUMEN SUMMARY

Zone	Lumens	%Luminaire
0-30°	896.30	79.50
0-40°	1041.31	92.40
0-60°	1119.62	99.30
0-90°	1127.35	100.00

PHOTOMETRIC REPORT

Product #: ET753
Wattage/Lumens: 28.7 W / 2250 lm
Luminaire LPW: 78 lm / W



CANDLE POWER SUMMARY

Degrees Vertical	0°
0	13984
5	10642
15	2926
25	848
35	268
45	109
55	48
65	20
75	9
85	4
90	3

ILLUMINANCE AT A DISTANCE


Distance to Target Plane	Footcandles Beam Center	Beam Diameter
4'	874	1.2'
6'	388	1.8'
8'	218	2.4'
10'	140	3.0'

ZONAL LUMEN SUMMARY

Zone	Lumens	%Luminaire
0-30°	1947.89	86.60
0-40°	2106.68	93.60
0-60°	2221.72	98.70
0-90°	2250.03	100.00

PHOTOMETRIC REPORT

Product #: ET754
Wattage/Lumens: 28.7 W / 2291 lm
Luminaire LPW: 80 lm / W



CANDLE POWER SUMMARY

Degrees Vertical	0°
0	6275
5	5884
15	3397
25	1206
35	273
45	99
55	44
65	20
75	9
85	3
90	2

ILLUMINANCE AT A DISTANCE

Distance to Target Plane	Footcandles Beam Center	Beam Diameter
4'	392	2.2'
6'	174	3.3'
8'	98.0	4.4'
10'	62.7	5.6'

ZONAL LUMEN SUMMARY


Zone	Lumens	%Luminaire
0-30°	1972.9	86.10
0-40°	2147.59	93.80
0-60°	2261.93	98.80
0-90°	2290.55	100.00

Photometrics

LED Track Fixtures

PHOTOMETRIC REPORT

Product #: ET755
 Wattage/Lumens: 28.6 W / 2181 lm
 Luminaire LPW: 76 lm / W



CANDLE POWER SUMMARY

Degrees Vertical	0°
0	4927
5	4693
15	3240
25	1212
35	356
45	133
55	56
65	25
75	10
85	3
90	2

ILLUMINANCE AT A DISTANCE


Distance to Target Plane	Footcandles Beam Center	Beam Diameter
4'	308	2.7'
6'	137	4.0'
8'	77.0	5.3'
10'	49.3	6.7'

ZONAL LUMEN SUMMARY

Zone	Lumens	%Luminaire
0-30°	1784.07	81.80
0-40°	1997.59	91.60
0-60°	2144.79	98.40
0-90°	2180.66	100.00

PHOTOMETRIC REPORT

Product #: ET756D
 Wattage/Lumens: 14.3 W / 1013 lm
 Luminaire LPW: 71 lm / W



CANDLE POWER SUMMARY

Degrees Vertical	0°
0	5005
5	4594
15	1708
25	373
35	66
45	18
55	5
65	2
75	1
85	1
90	1

ILLUMINANCE AT A DISTANCE


Distance to Target Plane	Footcandles Beam Center	Beam Diameter
4'	313	1.5'
6'	139	2.3'
8'	78.2	3.1'
10'	50.1	3.9'

ZONAL LUMEN SUMMARY

Zone	Lumens	%Luminaire
0-30°	937.43	92.50
0-40°	990	97.70
0-60°	1011.09	99.80
0-90°	1013.15	100.00

PHOTOMETRIC REPORT

Product #: ET757D
 Wattage/Lumens: 28.6 W / 2061 lm
 Luminaire LPW: 72 lm / W



CANDLE POWER SUMMARY

Degrees Vertical	0°
0	10180
5	9345
15	3475
25	758
35	134
45	37
55	10
65	4
75	3
85	1
90	1

ILLUMINANCE AT A DISTANCE

Distance to Target Plane	Footcandles Beam Center	Beam Diameter
4'	636	1.5'
6'	283	2.3'
8'	159	3.1'
10'	102	3.9'

ZONAL LUMEN SUMMARY


Zone	Lumens	%Luminaire
0-30°	1906.69	92.50
0-40°	2012.83	97.70
0-60°	2056.51	99.80
0-90°	2060.7	100.00

Photometrics

LED Wall Wash Track Fixtures

PHOTOMETRIC REPORT

Product #: ETW4030
 Wattage/Lumens: 31.4 W / 2439 lm
 Luminaire LPW: 78 lm / W



CANDLE POWER SUMMARY

Degrees Vertical	0°
0	995
5	990
15	970
25	840
35	709
45	558
55	403
65	251
75	104
85	15
90	3

ILLUMINANCE AT A DISTANCE


Distance to Target Plane	Footcandles Beam Center	Beam Diameter
4'	62.2	9.1'
6'	27.6	13.7'
8'	15.5	18.3'
10'	9.95	22.9'

ZONAL LUMEN SUMMARY

Zone	Lumens	%Luminaire
0-30°	746.87	30.60
0-40°	1195.33	49.00
0-60°	2009.73	82.40
0-90°	2438.51	100.00

PHOTOMETRIC REPORT

Product #: ETW4130
 Wattage/Lumens: 62 W / 4854 lm
 Luminaire LPW: 78 lm / W



CANDLE POWER SUMMARY

Degrees Vertical	0°
0	1970
5	1958
15	1856
25	1663
35	1405
45	1106
55	798
65	495
75	203
85	33
90	5

ILLUMINANCE AT A DISTANCE

Distance to Target Plane	Footcandles Beam Center	Beam Diameter
4'	123	9.1'
6'	54.7	13.7'
8'	30.8	18.3'
10'	19.7	22.9'

ZONAL LUMEN SUMMARY

Zone	Lumens	%Luminaire
0-30°	1480.41	30.50
0-40°	2370.55	48.80
0-60°	3989.58	82.20
0-90°	4853.88	100.00

Index

E10	80	EP666	23	EP841W-3A	69	ET532	32
E11	80	EP702	43	EP841W-4A	69	ET532-12	40
E12	80	EP800	72	EP841W-5A	69	ET532-18	40
E13	81	EP801	67	EP841W-7A	69	ET532-24	40
E20	82	EP802	67	EP841W-10A	69	ET532-36	40
E21	82	EP803	67	EP841W-12A	69	ET532-48	40
E22	82	EP804	67	EP844	73	ET532-75	32
E23	83	EP805	67	EP845	73	ET534	33
EC002	70	EP806	67	EP848	74	ET534-12	41
EC004	70	EP807	74	EP850	68	ET534-18	41
EC006	70	EP808	67	EP880	68	ET534-24	41
EC008	70	EP809	67	EP881	74	ET534-36	41
EC801	70	EP810	68	EP882	74	ET534-48	41
EC802	70	EP811	72	EP883	76, 77	ET535	33
EC803	70	EP812	68	EP884	76, 77	ET536	33
EC804	70	EP813	72	EP885	76, 77	ET537	33
EC805	70	EP814	72	EP900	43	ET539	33
EC806	70	EP815	72	EP901	73	ET539-75	33
EC808	70	EP816	73	EP903	73	ET540	33
EC809	70	EP817	68	EP904	73	ET541	34
EC812	71	EP818	74	EP905	74	ET544	34
EC817	71	EP819	73	EP906	74	ET546	34
EC840	71	EP820	20, 73	EP907	74	ET547	34
EC841	71	EP821	20, 34	EP918	74	ET548	35, 41
EC880	71	EP822	73	EP924	74	ET549	35
ECF	83	EP823	73	EP936	74	ET550	34
ECL	83	EP824	74	EP948	74	ET551	35
ECT	81	EP825	68	EP960	74	ET554	35
EDL30	84	EP827	68	EP979	68	ET558	36
EDL31	84	EP836	74	EP989	73	ET558-12	41
EDL60N	78	EP840B-1A	69	EP2015	83	ET558-18	41
EDL61N	78	EP840B-2A	69	ET128	42	ET558-24	41
EDL62N	79	EP840B-3A	69	ET132	42	ET558-36	41
EDL63N	79	EP840B-4A	69	ET169	42	ET558-48	41
EDL70	84	EP840B-5A	69	ET426	44	ET559	36
EDL71	84	EP840B-7A	69	ET428	44	ET562	36
EDL72	84	EP840B-10A	69	ET432	44	ET563	36
EDL73	84	EP840B-12A	69	ET502	31	ET565	37
EDL74	84	EP840BZ-1A	69	ET504	31	ET565-12	41
EDL75	84	EP840BZ-2A	69	ET505	31	ET565-18	41
EDL8030	76	EP840BZ-3A	69	ET507	31	ET565-24	41
EDL8040	76	EP840BZ-4A	69	ET526	31	ET565-36	41
EDL8130	76	EP840BZ-5A	69	ET526-12	40	ET565-48	41
EDL8140	76	EP840BZ-7A	69	ET526-18	40	ET566	38
EDL8230	77	EP840BZ-10A	69	ET526-24	40	ET567	38
EDL8240	77	EP840BZ-12A	69	ET526-36	40	ET568	38
EDL8330	77	EP840W-1A	69	ET526-48	40	ET570	37
EDL8340	77	EP840W-2A	69	ET526-75	31	ET578L30	6
ELW	83	EP840W-3A	69	ET527	31	ET579L30	15
EP002	67	EP840W-4A	69	ET528	32	ET579L35	15
EP004	67	EP840W-5A	69	ET528-12	40	ET579L40	15
EP006	67	EP840W-7A	69	ET528-18	40	ET580D	5
EP008	67	EP840W-10A	69	ET528-24	40	ET591	21
EP012	67	EP840W-12A	69	ET528-36	40	ET592	21
EP222	72	EP841B-1A	69	ET528-48	40	ET593	21
EP300	72	EP841B-2A	69	ET528-75	32	ET594D	22
EP322	18	EP841B-3A	69	ET529	32	ET597	22
EP323	19	EP841B-4A	69	ET530	32	ET598	6
EP324	19	EP841B-5A	69	ET530-12	40	ET599D	5
EP333	72	EP841B-7A	69	ET530-18	40	ET612D	7
EP422	72	EP841B-10A	69	ET530-24	40	ET613D	7
EP444	72	EP841B-12A	69	ET530-36	40	ET614D	8
EP555	23	EP841W-1A	69	ET530-48	40	ET615D	8
EP577	72	EP841W-2A	69	ET531	32	ET616-27D	9

Index

ET616-40D	9	ET744D	11	ETL2130	27
ET616D	9	ET745-35D	11	ETL2140	27
ET617-40D	9	ET745-40D	11	ETLD526	29
ET617D	9	ET745D	11	ETLD526-12	39
ET629	52	ET746-35D	11	ETLD526-18	39
ET630	52	ET746-40D	11	ETLD526-24	39
ET631	52	ET746D	11	ETLD526-36	39
ET633	52	ET750D	12	ETLD526-48	39
ET634	52	ET752D	12	ETLD528	29
ET635	52	ET753D	12	ETLD528-12	39
ET636	53	ET754D	12	ETLD528-18	39
ET637	53	ET755D	12	ETLD528-24	39
ET638	53	ET756D	13	ETLD528-36	39
ET639	53	ET757D	13	ETLD528-48	39
ET640	53	ET771	64	ETLD530	29
ET641	53	ET772	64	ETLD532	30
ET642	54	ET773	64	ETLD534	30
ET643	54	ET774	64	ETLD558	30
ET644	54	ET794	63	ETT	81
ET646	54	ET795	63	ETV	83
ET647	54	ET796	63	ETW4030	23
ET650	54	ET797	63	ETW4040	23
ET654	55	ET798	63	ETW4130	23
ET655	55	ET926	43	ETW4140	23
ET656	55	ET928	43	ETW4230	24
ET657	55	ET932	43	ETW4240	24
ET658	55	ET1135	61	ETW4330	24
ET659	55	ET1139	61	ETW4340	24
ET660	56	ET1158	61	ETW4430	25
ET661	56	ET1528	37	ETW4440	25
ET662	56	ET1603	46	MR120	44
ET665	60	ET1604	46	MR120-GU10	50
ET666	60	ET1625	46	MR120-GU10LD	50
ET667	60	ET1626	47		
ET668	56	ET1628	47		
ET669	56	ET1630	47		
ET673	56	ET1632	48		
ET674	57	ET1634	48		
ET675	57	ET1650	48		
ET676	57	ET1654	49		
ET677	57	ET1671	50		
ET681	57	ET1673	50		
ET682	57	ET1687	49		
ET685	58	ET1728	49		
ET686	58	ET61830D	16		
ET687	58	ET61930D	16		
ET690	58	ET62030D	17		
ET691	58	ET62040D	17		
ET692	58	ET62130D	17		
ET693	59	ET62140D	17		
ET694	59	ET62230D	18		
ET695	59	ET62330D	19		
ET696	59	ET62430D	19		
ET734	63	ET62530D	15		
ET735	63	ET62630D	15		
ET736	63	ET62730D	18		
ET740	10	ET62830D	20		
ET741	10	ET74730	10		
ET742	10	ET75830D	14		
ET743-35D	11	ET75930D	14		
ET743-40D	11	ETC420	62		
ET743D	11	ETC439	62		
ET744-35D	11	ETC454	62		
ET744-40D	11	ETC464	62		

ELCAT1058



Corporate Headquarters

2042 E. Vernon Ave.
Vernon, CA 90058
Tel: 323.231.2600
Fax: 323.231.3200
elcolighting.com

Customer Service

Tel: 800.522.2626
Fax: 800.644.2626
orderdesk@elcolighting.com
customerservice@elcolighting.com
sales@elcolighting.com

Printed in the U.S.A. 1/19
\$18.00

© ELCO Lighting. The marks appearing in this catalog are registered trademarks of ELCO Lighting. Other marks use herein are recognized trademarks of their respective companies. Products shown in this brochure may be covered by U.S. and international patents. Specifications subject to change without notice.