

FEB2017

Online Version Updated: **03/30/17**

MaxLite[®]

A NEW WAVE OF LIGHT



**NEW PRODUCT
SUPPLEMENT**

CONTROL SYSTEMS

- EnOcean Gateway Commissioning Software >1
- EnOcean LED Relay Node >1
- EnOcean Wireless Occupancy Sensors >1

- EnOcean Daylight Harvesting Sensor >1
- EnOcean Rocker Pad Wall Switches >1

INDOOR LED FIXTURES

- BayMAX™ LED Linear High Bays HL Series >2
- LED Low Voltage Light Bars >2
- TriMAX™ LED Vapor Tight Fixtures >2
- LED Linear Strip >2
- LED Linear Retrofit Strip >3
- LED Shop Light >3
- LED Residential Retrofits >4

- LED Downlight Retrofits >5
- LED T8 Lamp Ready Troffer >5
- FlatMAX® Edge Lit LED Flat Panels >6
- LED ECO-T 2X4 Recessed Troffer *(Pallet Quantity)* >7
- LED ECO Vapor Tight *(Pallet Quantity)* >7
- LED ECO Utility Wrap *(Pallet Quantity)* >7
- LED ECO Linear Strip Max Value *(Pallet Quantity)* >7

OUTDOOR LED FIXTURES

- Round Steel Poles >8
- Square Steel Poles >8
- LED Square Bollard Modern Series >8
- LED Round Bollard Classic Series >8
- LED Low-Profile Canopy Luminaires >9
- LED Low-Profile Parking Garage Canopy Luminaires >9
- LED Recessed Gas Canopy Fixture >9
- LED Slim Area Lights >9

- LED Vaporproof Jelly Jars >10
- Lamp Ready Jelly Jars E26 Socket >10
- LED Large Architectural Wall Pack >10
- LED X-Large Wall Pack >10
- StaxMAX™ High Output Flood Lights >11
- ModMAX™ High Voltage Flood Lights >11
- LED Hazardous Location Area Light >11

HORTICULTURE FIXTURES

- PhotonMAX™ Horticulture T8 Tube >12

- PhotonMAX™ Horticulture T8 Tube >12

GENERAL PURPOSE LAMPS

- LED Filament Lamps E26 Base >13
- LED Omni-Directional A Lamps >13
- LED Omni-Directional A Lamps Non-Dimmable >13
- LED Omni-Directional High CRI A Lamps >14
- LED Omni-Directional JA8 Certified A Lamps >14
- LED Omni-Directional JA8 Certified, Enclosed Rated A Lamps >14
- LED Omni-Directional Enclosed Rated A Lamps >15
- LED Warm-On-Dim BR Lamps >15
- LED PAR Lamps >15
- LED Candelabra B11 Lamps, Single & Multi Packs >16

- LED Globe Lamps, Single & Multi Packs >16
- LED Omni-Directional A Lamps >16
- Non-Dimmable, Multi Packs
- LED Area Lamp >16
- LED Direct Fit T8, Coated Glass >17
- LED Direct Fit T8, Plastic >17
- LED Direct Fit T5, Coated Glass >17
- LED Linear T8 Internal Driver Lamps, Glass >18
- LED T8 External Driver, Plastic >18
- External Driver >18
- LED PL DirectFit Retrofit Lamps >18

DISCONTINUED PRODUCTS >12

GTWENOCNNWC300U	
103512	
Type A	
902 MHz ERP2	
Integrated	
USB Bus Activity; LED Indicator	
Microsoft Windows	
FCC, IC, RoHS	

MODEL NUMBER
ORDER CODE
 USB Connector
 RF Standard
 Antenna
 Power Supply
 Operating System
CERTIFICATIONS

EnOcean Gateway Commissioning Software



REENOCNLEDRU	
103505	
120/277VAC, 60Hz	
16A @ 120/277 VAC	
EnOcean 902 MHz (IEEE 802.15.4)	
0-10V (Current Sink 35mA/Source 4mA)	
80 ft	
2.78" H x 1.65" W x 1.1" D	
UL, FCC, IC, RoHS	

MODEL NUMBER
ORDER CODE
 Power Supply
 Max Load
 RF Standard
 Dimming Compatible
 Transmission Range
 Dimensions
CERTIFICATIONS

EnOcean LED Relay Node



MSENOCNEOSWU	MSENOCNEOSCU
103507	103508
Indoor Light Energy Harvesting	Indoor Light Energy Harvesting
EnOcean 902 MHz (IEEE 802.15.4)	EnOcean 902 MHz (IEEE 802.15.4)
Wall	Ceiling
80 ft	80 ft
50 ft Wide Angle or 100 ft Long Range	34 ft Dia. @ 10 ft HT x 360°
5.83" L x 2.52" W x 1.8" D	6.30" L x 2.35" W x 1.47" D
FCC, IC, RoHS	FCC, IC, RoHS

MODEL NUMBER
ORDER CODE
 Power Supply
 RF Standard
 Mounting
 Transmission Range
 Detection Range
 Dimensions
CERTIFICATIONS

EnOcean Wireless Occupancy Sensors



MSENOCNELLSU	
103509	
Solar Energy Harvesting	
EnOcean 902 MHz (IEEE 802.15.4)	
Ceiling	
80 ft	
0-1020 Lux @ 50 Lux Steps	
6.30" L x 2.36" W x 1.15" D	
FCC, IC, RoHS	

MODEL NUMBER
ORDER CODE
 Power Supply
 RF Standard
 Mounting
 Transmission Range
 Lux Detection (Rate)
 Dimensions
CERTIFICATIONS

EnOcean Daylight Harvesting Sensor



WSENOCNESRPU	WSENOCNEDRPU
103510	103511
Mechanical Energy Harvesting	Mechanical Energy Harvesting
902 MHz	902 MHz
1 Button Dimming Rocker Switch (White)	2 Button Dimming Rocker Switch (White)
80 ft	80 ft
4.95" H x 3.21" W x 0.74" D	4.95" H x 4.52" W x 0.72" D
FCC, IC, RoHS	FCC, IC, RoHS

MODEL NUMBER
ORDER CODE
 Power Supply
 RF Standard
 Number of Switches
 Transmission Range
 Dimensions
CERTIFICATIONS

EnOcean Rocker Pad Wall Switches



BayMAX™ LED Linear High Bays HL Series



MODEL NUMBER	HL-100UW-50	HL-150UW-50	HL-200UW-50
ORDER CODE	101446	101448	101450
Input Wattage	100W	150W	200W
Voltage	120-277V	120-277V	120-277V
Delivered Lumens (lm)	13,400 lm	19,500 lm	25,000 lm
Efficacy (lm/W)	129 lm/W	130 lm/W	128 lm/W
Color Rendering Index (CRI)	≥70	≥70	≥70
Color Temperature (CCT)	5000K	5000K	5000K
Replacement	4 x 54W T5HO	6 x 54W T5HO	8 x 54W T5HO
Dimming Compatible	0-10V	0-10V	0-10V
Lumen Maintenance (L70)	100,000 hours	100,000 hours	100,000 hours
CERTIFICATIONS	cULus (Damp Listed), DLC Premium, FCC	cULus (Damp Listed), DLC Premium, FCC	cULus (Damp Listed), DLC Premium, FCC

LED Low Voltage Light Bars



MODEL NUMBER	12LBLV40	24LBLV40	36LBLV40	48LBLV40
ORDER CODE	96478	96480	96482	96484
Input Wattage	6W	10W	15W	18W
Voltage	24V DC	24V DC	24V DC	24V DC
Delivered Lumens (lm)	300 lm	580 lm	850 lm	1,020 lm
Efficacy (lm/W)	56 lm/W	59 lm/W	58 lm/W	57 lm/W
Color Rendering Index (CRI)	≥80	≥80	≥80	≥80
Color Temperature (CCT)	4000K	4000K	4000K	4000K
Dimming Compatible	Proprietary Dimmer Accessory	Proprietary Dimmer Accessory	Proprietary Dimmer Accessory	Proprietary Dimmer Accessory
Lumen Maintenance (L70)	50,000 hours	50,000 hours	50,000 hours	50,000 hours
CERTIFICATIONS	cULus (Damp Listed), RoHS	cULus (Damp Listed), RoHS	cULus (Damp Listed), RoHS	cULus (Damp Listed), RoHS

TriMAX™ LED Vapor Tight Fixtures



MODEL NUMBER	VT-V4840U-40	VT-V4840U-50	VT-V4860U-40	VT-V4860U-50
ORDER CODE	101636	101637	101638	101639
Input Wattage	40W	40W	60W	60W
Voltage	120-277V	120-277V	120-277V	120-277V
Delivered Lumens (lm)	4,550 lm	4,550 lm	7,360 lm	7,360 lm
Efficacy (lm/W)	119 lm/W	119 lm/W	119 lm/W	119 lm/W
Color Rendering Index (CRI)	≥80	≥80	≥80	≥80
Color Temperature (CCT)	4000K	5000K	4000K	5000K
Replacement	3 x 32W T8 or 1 x 54W T5HO	3 x 32W T8 or 1 x 54W T5HO	4 x 32W T8 or 2 x 54W T5HO	4 x 32W T8 or 2 x 54W T5HO
Dimming Compatible	0-10V	0-10V	0-10V	0-10V
Lumen Maintenance (L70)	50,000 hours	50,000 hours	50,000 hours	50,000 hours
CERTIFICATIONS	cETLus (Wet Listed), ETL Sanitation, FCC, DLC Premium, RoHS	cETLus (Wet Listed), ETL Sanitation, FCC, DLC Premium, RoHS	cETLus (Wet Listed), ETL Sanitation, FCC, DLC Premium, RoHS	cETLus (Wet Listed), ETL Sanitation, FCC, DLC Premium, RoHS

LED Linear Strip



MODEL NUMBER	LS-4824U-50	LS-4836U-50
ORDER CODE	102380	102381
Input Wattage	24W	36W
Voltage	120-277V	120-277V
Delivered Lumens (lm)	2,500 lm	3,700 lm
Efficacy (lm/W)	114 lm/W	115 lm/W
Color Rendering Index (CRI)	≥80	≥80
Color Temperature (CCT)	5000K	5000K
Replacement	1 x 32W T8	2 x 32W T8
Dimming Compatible	0-10V	0-10V
Lumen Maintenance (L70)	50,000 hours	50,000 hours
CERTIFICATIONS	cULus (Damp Listed), DLC Premium, RoHS	cULus (Damp Listed), DLC Premium, RoHS

LED Linear Retrofit Strip

RS-4824U-50	RS-4836U-50
102378	102379
24W	36W
120-277V	120-277V
2,400 lm	3,600 lm
108 lm/W	112 lm/W
≥80	≥80
5000K	5000K
1 x 32W T8	2 x 32W T8
0-10V	0-10V
50,000 hours	50,000 hours
cULus (Damp Listed), DLC Premium, FCC, RoHS	cULus (Damp Listed), DLC Premium, FCC, RoHS

MODEL NUMBER
ORDER CODE
 Input Wattage
 Voltage
 Delivered Lumens (lm)
 Efficacy (lm/W)
 Color Rendering Index (CRI)
 Color Temperature (CCT)
 Replacement
 Dimming Compatible
 Lumen Maintenance (L70)
CERTIFICATIONS



SL-48401-50
107705
40W
120V
4,100 lm
103 lm/W
≥80
5000K
2 x 32W T8
No
50,000 hours
cETLus, RoHS, ENERGY STAR®

MODEL NUMBER
ORDER CODE
 Input Wattage
 Voltage
 Delivered Lumens (lm)
 Efficacy (lm/W)
 Color Rendering Index (CRI)
 Color Temperature (CCT)
 Replacement
 Dimming Compatible
 Lumen Maintenance (L70)
CERTIFICATIONS



LED Linear Strip LS Series

Architectural, economical and compact, the LS Series LED Strip is the perfect linear lighting solution for commercial, industrial, retail and residential applications.

- **4' linear fixture**
- **24W and 36W available**
- **DLC Premium qualified**
- **Surface, pendant or stem mount**

MaxLite
 A NEW WAVE OF LIGHT
www.maxlite.com

Retrofit Kit also available - converts 4' / 8' fluorescent strips to LED in minutes!

Right In Line



LED 4" Residential Retrofit



MODEL NUMBER	RR41027W-L7
ORDER CODE	107301
Input Wattage	10W
Voltage	120V
Delivered Lumens (lm)	720 lm
Efficacy (lm/W)	75 lm/W
Color Rendering Index (CRI)	≥80
Color Temperature (CCT)	2700K
Replacement	60W INC
Dimming Compatible	Triac dimmable
Lumen Maintenance (L70)	36,000 hours
CERTIFICATIONS	cULus, ENERGY STAR®, FCC, RoHS

LED 4" High CRI Residential Retrofit



MODEL NUMBER	RR41027WC-L7
ORDER CODE	107305
Input Wattage	10W
Voltage	120V
Delivered Lumens (lm)	680 lm
Efficacy (lm/W)	69 lm/W
Color Rendering Index (CRI)	90
Color Temperature (CCT)	2700K
Replacement	60W INC
Dimming Compatible	Triac dimmable
Lumen Maintenance (L70)	36,000 hours
CERTIFICATIONS	cULus, ENERGY STAR®, FCC, RoHS

LED 6" Residential Retrofit



MODEL NUMBER	RR61127W-L7	RR61130W-L7	RR61827W-L7	RR61830W-L7
ORDER CODE	107309	107310	107317	107318
Input Wattage	11W	11W	18W	18W
Voltage	120V	120V	120V	120V
Delivered Lumens (lm)	880 lm	880 lm	1,370 lm	1,370 lm
Efficacy (lm/W)	80 lm/W	80 lm/W	76 lm/W	76 lm/W
Color Rendering Index (CRI)	≥80	≥80	≥80	≥80
Color Temperature (CCT)	2700K	3000K	2700K	3000K
Replacement	75W INC	75W INC	120W INC	120W INC
Dimming Compatible	Triac dimmable	Triac dimmable	Triac dimmable	Triac dimmable
Lumen Maintenance (L70)	36,000 hours	36,000 hours	36,000 hours	36,000 hours
CERTIFICATIONS	cULus, ENERGY STAR®, FCC, RoHS	cULus, ENERGY STAR®, FCC, RoHS	cULus, ENERGY STAR®, FCC, RoHS	cULus, ENERGY STAR®, FCC, RoHS

LED 6" High CRI Residential Retrofit



MODEL NUMBER	RR61827WC-L7	RR61830WC-L7
ORDER CODE	107321	107322
Input Wattage	18W	18W
Voltage	120V	120V
Delivered Lumens (lm)	1,290 lm	1,290 lm
Efficacy (lm/W)	74 lm/W	74 lm/W
Color Rendering Index (CRI)	≥90	≥90
Color Temperature (CCT)	2700K	3000K
Replacement	120W INC	120W INC
Dimming Compatible	Triac dimmable	Triac dimmable
Lumen Maintenance (L70)	36,000 hours	36,000 hours
CERTIFICATIONS	cULus, ENERGY STAR®, FCC, RoHS	cULus, ENERGY STAR®, FCC, RoHS

LED 4" Downlight Retrofit

RR-409U-30W	RR-409U-40W	RR-409U-50W
102382	107285	107287
9W	9W	9W
120-277V	120-277V	120-277V
680 lm	720 lm	760 lm
85 lm/W	86 lm/W	86 lm/W
≥80	≥80	≥80
3000K	4000K	5000K
60W INC	60W INC	60W INC
Triac dimmable	Triac dimmable	Triac dimmable
50,000 hours	50,000 hours	50,000 hours
cULus, ENERGY STAR®, FCC, RoHS	cULus, ENERGY STAR®, FCC, RoHS	cULus, ENERGY STAR®, FCC, RoHS

MODEL NUMBER
ORDER CODE
 Input Wattage
 Voltage
 Delivered Lumens (lm)
 Efficacy (lm/W)
 Color Rendering Index (CRI)
 Color Temperature (CCT)
 Replacement
 Dimming Compatible
 Lumen Maintenance (L70)

CERTIFICATIONS



4"



RR-613U-30W	RR-613U-40W	RR-613U-50W
102383	107286	107288
13W	13W	13W
120-277V	120-277V	120-277V
1,110 lm	1,180 lm	1,250 lm
97 lm/W	98 lm/W	99 lm/W
≥80	≥80	≥80
3000K	4000K	5000K
120W INC	120W INC	120W INC
Triac dimmable	Triac dimmable	Triac dimmable
50,000 hours	50,000 hours	50,000 hours
cULus, ENERGY STAR®, FCC, RoHS	cULus, ENERGY STAR®, FCC, RoHS	cULus, ENERGY STAR®, FCC, RoHS

MODEL NUMBER
ORDER CODE
 Input Wattage
 Voltage
 Delivered Lumens (lm)
 Efficacy (lm/W)
 Color Rendering Index (CRI)
 Color Temperature (CCT)
 Replacement
 Dimming Compatible
 Lumen Maintenance (L70)

CERTIFICATIONS

LED 6" Downlight Retrofit



6"



MLRT22XT8	MLRT24XT8
97869	97870
4x T8 LED*	4x T8 LED*
120-277V	120-277V
10W Per Lamp	22W Per Lamp
cULus (Damp Listed), RoHS	cULus (Damp Listed), RoHS

MODEL NUMBER
ORDER CODE
 Number of Lamps
 Voltage
 Max Wattage
CERTIFICATIONS

LED T8 Lamp Ready Troffer



2'x2'
2'x4'



*Lamps not included. See Pages 83-85 of main catalog for compatible T8 lamps.

FlatMAX® Edge Lit LED Flat Panels




MODEL NUMBER	MLFP22EP3035	MLFP22EP3041	MLFP22EP3050
ORDER CODE	105920	105921	105922
Input Wattage	30W	30W	30W
Voltage	120-277V	120-277V	120-277V
Delivered Lumens (lm)	3,600 lm	3,680 lm	3,710 lm
Efficacy (lm/W)	118 lm/W	120 lm/W	122 lm/W
Color Rendering Index (CRI)	≥80	≥80	≥80
Color Temperature (CCT)	3500K	4100K	5000K
Replacement	3 x 17W T8	3 x 17W T8	3 x 17W T8
Dimming Compatible	0-10V	0-10V	0-10V
Lumen Maintenance (L70)	50,000 hours	50,000 hours	50,000 hours
CERTIFICATIONS	cULus (Damp Listed), FCC, RoHS, DLC Premium	cULus (Damp Listed), FCC, RoHS, DLC Premium	cULus (Damp Listed), FCC, RoHS, DLC Premium

FlatMAX® Edge Lit LED Flat Panels




MODEL NUMBER	MLFP22EP3535	MLFP22EP3541	MLFP22EP3550
ORDER CODE	107699	107700	107701
Input Wattage	35W	35W	35W
Voltage	120-277V	120-277V	120-277V
Delivered Lumens (lm)	4,440 lm	4,550 lm	4,640 lm
Efficacy (lm/W)	127 lm/W	127 lm/W	129 lm/W
Color Rendering Index (CRI)	≥80	≥80	≥80
Color Temperature (CCT)	3500K	4100K	5000K
Replacement	4 x 17W T8	4 x 17W T8	4 x 17W T8
Dimming Compatible	0-10V	0-10V	0-10V
Lumen Maintenance (L70)	50,000 hours	50,000 hours	50,000 hours
CERTIFICATIONS	cULus (Damp Listed), FCC, RoHS, DLC Premium	cULus (Damp Listed), FCC, RoHS, DLC Premium	cULus (Damp Listed), FCC, RoHS, DLC Premium

FlatMAX® Edge Lit LED Flat Panels



MODEL NUMBER	MLFP24EP4035	MLFP24EP4041	MLFP24EP4050
ORDER CODE	105926	105927	105928
Input Wattage	40W	40W	40W
Voltage	120-277V	120-277V	120-277V
Delivered Lumens (lm)	4,440 lm	4,640 lm	4,770 lm
Efficacy (lm/W)	118 lm/W	121 lm/W	124 lm/W
Color Rendering Index (CRI)	≥80	≥80	≥80
Color Temperature (CCT)	3500K	4100K	5000K
Replacement	3 x 32W T8	3 x 32W T8	3 x 32W T8
Dimming Compatible	0-10V	0-10V	0-10V
Lumen Maintenance (L70)	50,000 hours	50,000 hours	50,000 hours
CERTIFICATIONS	cULus (Damp Listed), FCC, RoHS, DLC Premium	cULus (Damp Listed), FCC, RoHS, DLC Premium	cULus (Damp Listed), FCC, RoHS, DLC Premium

FlatMAX® Edge Lit LED Flat Panels



MODEL NUMBER	MLFP24EP4835	MLFP24EP4841	MLFP24EP4850
ORDER CODE	107702	107703	107704
Input Wattage	48W	48W	48W
Voltage	120-277V	120-277V	120-277V
Delivered Lumens (lm)	5,700 lm	5,810 lm	6,030 lm
Efficacy (lm/W)	129 lm/W	130 lm/W	134 lm/W
Color Rendering Index (CRI)	≥80	≥80	≥80
Color Temperature (CCT)	3500K	4100K	5000K
Replacement	4 x 32W T8	4 x 32W T8	4 x 32W T8
Dimming Compatible	0-10V	0-10V	0-10V
Lumen Maintenance (L70)	50,000 hours	50,000 hours	50,000 hours
CERTIFICATIONS	cULus (Damp Listed), FCC, RoHS, DLC Premium	cULus (Damp Listed), FCC, RoHS, DLC Premium	cULus (Damp Listed), FCC, RoHS, DLC Premium

LED ECO-T 2X4
Recessed Troffer
 (Pallet Quantity)

MLRT24N4240-P	
107673	
42W	
120-277V	
4,520 lm	
107 lm/W	
≥80	
4000K	
3 x 32W T8	
No	
50,000 hours	
cULus, FCC, RoHS, DLC	

MODEL NUMBER
ORDER CODE
Input Wattage
Voltage
Delivered Lumens (lm)
Efficacy (lm/W)
Color Rendering Index (CRI)
Color Temperature (CCT)
Replacement
Dimming Compatible
Lumen Maintenance (L70)
CERTIFICATIONS



LED ECO
Vapor Tight
 (Pallet Quantity)

LSVECO-4NU4040-P	LSVECO-4NU4050-P
107668	107669
40W	40W
120-277V	120-277V
4,300 lm	4,360 lm
114 lm/W	116 lm/W
≥80	≥80
4000K	5000K
3 x 32W T8	3 x 32W T8
No	No
50,000 hours	50,000 hours
cULus, FCC, RoHS, DLC	cULus, FCC, RoHS, DLC

MODEL NUMBER
ORDER CODE
Input Wattage
Voltage
Delivered Lumens (lm)
Efficacy (lm/W)
Color Rendering Index (CRI)
Color Temperature (CCT)
Replacement
Dimming Compatible
Lumen Maintenance (L70)
CERTIFICATIONS



LED ECO
Utility Wrap
 (Pallet Quantity)

LSUECO-4NU4040-P	LSUECO-4NU4050-P
107666	107667
40W	40W
120-277V	120-277V
4,330 lm	4,320 lm
108 lm/W	105 lm/W
≥80	≥80
4000K	5000K
3 x 32W T8	3 x 32W T8
No	No
50,000 hours	50,000 hours
cULus, FCC, RoHS, DLC	cULus, FCC, RoHS, DLC

MODEL NUMBER
ORDER CODE
Input Wattage
Voltage
Delivered Lumens (lm)
Efficacy (lm/W)
Color Rendering Index (CRI)
Color Temperature (CCT)
Replacement
Dimming Compatible
Lumen Maintenance (L70)
CERTIFICATIONS



LED ECO Linear Strip
Max Value
 (Pallet Quantity)

LSECO-4NU2050-P	
107671	
40W	
120-277V	
4,200 lm	
105 lm/W	
≥80	
5000K	
1 x 75W T12HO	
No	
50,000 hours	
cULus, FCC, RoHS, DLC	

MODEL NUMBER
ORDER CODE
Input Wattage
Voltage
Delivered Lumens (lm)
Efficacy (lm/W)
Color Rendering Index (CRI)
Color Temperature (CCT)
Replacement
Dimming Compatible
Lumen Maintenance (L70)
CERTIFICATIONS



Specs shown are for the 8ft version, which is two of the 4ft versions connected together.

Round Steel Poles



MODEL NUMBER	PL-RD12S-B	PL-RD20S-B	PL-RD25S-B
ORDER CODE	102215	102218	102221
Length	12'	20'	25'
Diameter	4"	4"	4"
Finish	Bronze	Bronze	Bronze

Black and white finishes also available. List of compatible accessories can be found on maxlite.com.

Square Steel Poles



MODEL NUMBER	PL-SQ12S-B	PL-SQ20S-B	PL-SQ25S-B	PL-SQ30S-B
ORDER CODE	102203	102206	102209	102212
Length	12'	20'	25'	30'
Dimensions	4"x4"	4"x4"	4"x4"	5"x5"
Finish	Bronze	Bronze	Bronze	Bronze

Black and white finishes also available. List of compatible accessories can be found on maxlite.com.

LED Square Bollard Modern Series



MODEL NUMBER	BL-MOSQ17U-50B
ORDER CODE	107257
Input Wattage	17W
Voltage	120-277V
Delivered Lumens (lm)	480 lm
Efficacy (lm/W)	270 lm/W
Color Rendering Index (CRI)	85
Color Temperature (CCT)	5000K
Finish	Bronze
Dimming Compatible	0-10V
Lumen Maintenance (L70)	50,000 hours
CERTIFICATIONS	cCSAus (Wet Listed)

Black and white finishes also available. 4000K also available.

LED Round Bollard Classic Series



MODEL NUMBER	BL-CLRD17-40B
ORDER CODE	107253
Input Wattage	17W
Voltage	120-277V
Delivered Lumens (lm)	1225 lm
Efficacy (lm/W)	70 lm/W
Color Rendering Index (CRI)	85
Color Temperature (CCT)	4000K
Finish	Bronze
Dimming Compatible	0-10V
Lumen Maintenance (L70)	50,000 hours
CERTIFICATIONS	cCSAus (Wet Listed)



CPL30AUC50B	CPL40AUC50B	CPL58AUC50B
102005	102010	102335
30W	40W	58W
120-277V	120-277V	120-277V
2,690 lm	3,845 lm	5,100 lm
91 lm/W	94 lm/W	99 lm/W
≥75	≥75	≥75
5000K	5000K	5000K
150W MH	175W MH	250W MH
0-10V	0-10V	0-10V
≥100,000 hours	≥100,000 hours	≥100,000 hours
cULus (Wet Listed), FCC	cULus (Wet Listed), DLC, FCC	cULus (Wet Listed), FCC

MODEL NUMBER
ORDER CODE
 Input Wattage
 Voltage
 Delivered Lumens (lm)
 Efficacy (lm/W)
 Color Rendering Index (CRI)
 Color Temperature (CCT)
 Replacement
 Dimming Compatible
 Lumen Maintenance (L70)
CERTIFICATIONS



CPL30UP50B	CPL40AUP50B	CPL58AUP50B
102001	101024	102339
30W	41W	53W
120-277V	120-277V	120-277V
2,895 lm	4,060 lm	5,450 lm
97 lm/W	96 lm/W	104 lm/W
≥75	≥75	≥75
5000K	5000K	5000K
150W MH	175W MH	250W MH
0-10V	0-10V	0-10V
≥100,000 hours	≥100,000 hours	≥100,000 hours
cULus (Wet Listed), DLC, FCC	cULus (Wet Listed), DLC, FCC	cULus (Wet Listed), DLC, FCC

MODEL NUMBER
ORDER CODE
 Input Wattage
 Voltage
 Delivered Lumens (lm)
 Efficacy (lm/W)
 Color Rendering Index (CRI)
 Color Temperature (CCT)
 Replacement
 Dimming Compatible
 Lumen Maintenance (L70)
CERTIFICATIONS



RCX080AU50W
101319
80W
120-277V
10,910 lm
132 lm/W
≥80
5000K
320W MH
0-10V
≥100,000 hours
ETL (Wet Listed), DLC Premium, FCC, RoHS

MODEL NUMBER
ORDER CODE
 Input Wattage
 Voltage
 Delivered Lumens (lm)
 Efficacy (lm/W)
 Color Rendering Index (CRI)
 Color Temperature (CCT)
 Replacement
 Dimming Compatible
 Lumen Maintenance (L70)
CERTIFICATIONS



AR-MAL6OUT3-50BR	AR-MAL10OUT3-50BR	AR-MAL14OUT3-50BR	AR-MAL28OUT3-50BR
103544	103553	103562	103571
60W	100W	140W	280W
120-277V	120-277V	120-277V	120-277V
7,725 lm	12,360 lm	17,120 lm	31,015 lm
129 lm/W	129 lm/W	126 lm/W	114 lm/W
≥75	≥75	≥75	≥75
5000K	5000K	5000K	5000K
150W PSMH	250W PSMH	400W PSMH	750W PSMH
Yes	Yes	Yes	Yes
100,000 hours	100,000 hours	100,000 hours	100,000 hours
cULus (Wet Listed), DLC Premium	cULus (Wet Listed), DLC Premium	cULus (Wet Listed), DLC Premium	cULus (Wet Listed), DLC Premium

MODEL NUMBER
ORDER CODE
 Input Wattage
 Voltage
 Delivered Lumens (lm)
 Efficacy (lm/W)
 Color Rendering Index (CRI)
 Color Temperature (CCT)
 Replacement
 Dimming Compatible
 Lumen Maintenance (L70)
CERTIFICATIONS



4000K, Type V, and 347-480V available. Please visit [maxlite.com](http://www.maxlite.com) for more details.

LED Vaporproof Jelly Jars



MODEL NUMBER	JJ12A150GW0	JJ12A150GCO
ORDER CODE	101032	101033
Input Wattage	12W	12W
Voltage	120-277V	120-277V
Delivered Lumens (lm)	705 lm	720 lm
Efficacy (lm/W)	62 lm/W	64 lm/W
Color Rendering Index (CRI)	≥70	≥70
Color Temperature (CCT)	5000K	5000K
Replacement	60W INC	60W INC
Mount	Wall Mount	Ceiling Mount
Dimming Compatible	0-10V	0-10V
Lumen Maintenance (L70)	80,000 hours	80,000 hours
CERTIFICATIONS	cULus (Wet Listed), RoHS	cULus (Wet Listed), RoHS

Lamp Ready Jelly Jars E26 Socket



MODEL NUMBER	JJC12001	JJP12001	JJW12001
ORDER CODE	101443	101441	101439
Input Wattage	100W Input	100W Input	100W Input
Voltage	120-277V	120-277V	120-277V
Mount	Ceiling Mount	Pendant Mount	Wall Mount
Dimming Compatible	Lamp & Control Dependent	Lamp & Control Dependent	Lamp & Control Dependent
Lumen Maintenance (L70)	25,000 hours	25,000 hours	25,000 hours
CERTIFICATIONS	cULus (Wet Listed)	cULus (Wet Listed)	cULus (Wet Listed)

LED Large Architectural Wall Pack



MODEL NUMBER	WP-WMP30UT2-50B	WP-WMP60UT2-50B	WP-WMP90UT2-50B
ORDER CODE	101373	101374	101375
Input Wattage	30W	60W	90W
Voltage	120-277V	120-277V	120-277V
Delivered Lumens (lm)	3,035 lm	5,855 lm	8,600 lm
Efficacy (lm/W)	97 lm/W	102 lm/W	102 lm/W
Color Rendering Index (CRI)	≥75	≥75	≥75
Color Temperature (CCT)	5000K	5000K	5000K
Replacement	175W MH	250W MH	400W MH
Dimming Compatible	0-10V	0-10V	0-10V
Lumen Maintenance (L70)	100,000 hours	100,000 hours	100,000 hours
CERTIFICATIONS	cULus (Wet Listed), DLC, FCC	cULus (Wet Listed), DLC, FCC	cULus (Wet Listed), DLC, FCC

LED X-Large Wall Pack



MODEL NUMBER	WP-OPX120UT3-50B
ORDER CODE	101359
Input Wattage	120W
Voltage	120-277V
Delivered Lumens (lm)	15,570 lm
Efficacy (lm/W)	130 lm/W
Color Rendering Index (CRI)	85
Color Temperature (CCT)	5000K
Replacement	400W MH
Dimming Compatible	0-10V
Lumen Maintenance (L70)	100,000 hours
CERTIFICATIONS	cULus (Damp Listed), DLC, RoHS

StaxMAX™ High Output Flood Lights



ELLF1804W50	ELLF3604W50	ELLF5404W50
107165	107171	107177
175W	346W	518W
347-480V	347-480V	347-480V
20,220 lm	40,060 lm	59,905 lm
116 lm/W	116 lm/W	115 lm/W
≥80	≥80	≥80
5000K	5000K	5000K
400W MH	1000W MH	1500W MH
0-10V	0-10V	0-10V
60,000 hours	60,000 hours	60,000 hours
cULus (Wet Listed), DLC, FCC	cULus (Wet Listed), DLC, FCC	cULus (Wet Listed), DLC, FCC

MODEL NUMBER
ORDER CODE
 Input Wattage
 Voltage
 Delivered Lumens (lm)
 Efficacy (lm/W)
 Color Rendering Index (CRI)
 Color Temperature (CCT)
 Replacement
 Dimming Compatible
 Lumen Maintenance (L70)
CERTIFICATIONS



ModMAX™ High Voltage Flood Lights



MM210HW50FDG	MM420HW50FDG	MM630HW50FDG
107331	107332	107333
218W	445W	629W
120-277V	120-277V	120-277V
20,220 lm	38,475 lm	62,260 lm
118 lm/W	114 lm/W	106 lm/W
92	86	99
5000K	5000K	5000K
400W MH	1000W MH	1500W MH
No	No	No
100,000 hours	100,000 hours	100,000 hours
cULus (Wet Listed), FCC	cULus (Wet Listed), FCC	cULus (Wet Listed), FCC

MODEL NUMBER
ORDER CODE
 Input Wattage
 Voltage
 Delivered Lumens (lm)
 Efficacy (lm/W)
 Color Rendering Index (CRI)
 Color Temperature (CCT)
 Replacement
 Dimming Compatible
 Lumen Maintenance (L70)
CERTIFICATIONS



LED Hazardous Location Area Light



HL-AR80UW-50G	HL-AR150UW-50G
107618	107620
80W	150W
120-277V	120-277V
9,600 lm	18,245 lm
120 lm/W	120 lm/W
≥70	≥70
5000K	5000K
250W MH	400W MH
No	No
100,000 hours	100,000 hours
cULus (Wet Listed), DLC Premium	cULus (Wet Listed), DLC Premium

MODEL NUMBER
ORDER CODE
 Input Wattage
 Voltage
 Delivered Lumens (lm)
 Efficacy (lm/W)
 Color Rendering Index (CRI)
 Color Temperature (CCT)
 Replacement
 Dimming Compatible
 Lumen Maintenance (L70)
CERTIFICATIONS



PhotonMAX™ Horticulture T8 Tube



MODEL NUMBER	L18T8SE415
ORDER CODE	102185
Input Wattage	18W
Voltage	120-277V
Coverage Area (m ²)	0.4M, 1.3ft mounting height = 1.66 m ²
PAR Output (μmol/s)	25 μmol/s
PPFD (μmol/m ² /s)	0.4M, 1.3ft mounting height = 25 μmol/m ² /s
Replacement	32W FLUOR
Lumen Maintenance (L70)	25,000 hours
CERTIFICATIONS	UL Classified (Damp Listed), RoHS, FCC

LED T8 Lamp Ready High Bay Fixture



48"



MODEL NUMBER	BLHT4XT8USE4810	BLHT6XT8USE4815	BLHT8XT8USE4820
ORDER CODE	75428	75429	75430
Number of Lamps	4x T8 LED*	6x T8 LED*	8x T8 LED*
Voltage	120-277V	120-277V	120-277V
Max Wattage	22W Per Lamp	22W Per Lamp	22W Per Lamp
CERTIFICATIONS	cULus (Damp Listed)	cULus (Damp Listed)	cULus (Damp Listed)

*Lamps not included.

MaxLite
A NEW WAVE OF LIGHT

Ready, Set, Glow.

LED T8 Lamp Ready Fixtures

F4B10DLED27	F7A19DLED27	F7.5G25DLED27	V5ST19DLED22
103590	107237	103592	107199
4W	7W	7.5W	5W
120V	120V	120V	120V
330 lm	800 lm	800 lm	320 lm
83 lm/W	114 lm/W	107 lm/W	64 lm/W
82	82	80	81
2700K	2700K	2700K	2200K
40W INC	60W INC	100W INC	40W INC
Yes	Yes	Yes	Yes
15,000 hours	15,000 hours	15,000 hours	15,000 hours
cULus, ENERGY STAR®	cULus, ENERGY STAR®	cULus, ENERGY STAR®	cULus, ENERGY STAR®

MODEL NUMBER
ORDER CODE
 Input Wattage
 Voltage
 Delivered Lumens (lm)
 Efficacy (lm/W)
 Color Rendering Index (CRI)
 Color Temperature (CCT)
 Replacement
 Dimming Compatible
 Lumen Maintenance (L70)
CERTIFICATIONS



6A19DLED27/G4	9A19DLED27/G4	11A19DLED27/G4	15A21DLED27/G4
101464	101466	101432	101434
6W	9W	11W	15W
120V	120V	120V	120V
480 lm	800 lm	1100 lm	1600 lm
80 lm/W	88 lm/W	100 lm/W	106 lm/W
≥80	≥80	≥80	≥80
2700K	2700K	2700K	2700K
40W INC	60W INC	75W INC	100W INC
Yes	Yes	Yes	Yes
25,000 hours	25,000 hours	25,000 hours	25,000 hours
cULus, RoHS, ENERGY STAR®	cULus, RoHS, ENERGY STAR®	cULus, RoHS, ENERGY STAR®	cULus, RoHS, ENERGY STAR®

MODEL NUMBER
ORDER CODE
 Input Wattage
 Voltage
 Delivered Lumens (lm)
 Efficacy (lm/W)
 Color Rendering Index (CRI)
 Color Temperature (CCT)
 Replacement
 Dimming Compatible
 Lumen Maintenance (L70)
CERTIFICATIONS

LED Omni-Directional A Lamps E26 Base



6A19GUDLED27/G4	9A19GUDLED27/G4	11A19GUDLED27/G4	15A21GUDLED27/G4
102030	102165	102197	102200
6W	9W	11W	15W
120V	120V	120V	120V
480 lm	800 lm	1100 lm	1600 lm
80 lm/W	88 lm/W	100 lm/W	106 lm/W
≥80	≥80	≥80	≥80
2700K	2700K	2700K	2700K
40W INC	60W INC	75W INC	100W INC
Yes	Yes	Yes	Yes
25,000 hours	25,000 hours	25,000 hours	25,000 hours
cULus, RoHS, ENERGY STAR®	cULus, RoHS, ENERGY STAR®	cULus, RoHS, ENERGY STAR®	cULus, RoHS, ENERGY STAR®

MODEL NUMBER
ORDER CODE
 Input Wattage
 Voltage
 Delivered Lumens (lm)
 Efficacy (lm/W)
 Color Rendering Index (CRI)
 Color Temperature (CCT)
 Replacement
 Dimming Compatible
 Lumen Maintenance (L70)
CERTIFICATIONS

LED Omni-Directional A Lamps GU24 Base



6A19ND27	9A19ND27	11A19ND27	14A19ND27
102327	102329	102331	102333
6W	9W	11W	14W
120V	120V	120V	120V
480 lm	800 lm	1100 lm	1600 lm
80 lm/W	89 lm/W	100 lm/W	114 lm/W
≥82	≥82	≥82	≥82
2700K	2700K	2700K	2700K
40W INC	60W INC	75W INC	100W INC
No	No	No	No
15,000 hours	15,000 hours	15,000 hours	15,000 hours
cULus, RoHS, ENERGY STAR®	cULus, RoHS, ENERGY STAR®	cULus, RoHS, ENERGY STAR®	cULus, RoHS, ENERGY STAR®

MODEL NUMBER
ORDER CODE
 Input Wattage
 Voltage
 Delivered Lumens (lm)
 Efficacy (lm/W)
 Color Rendering Index (CRI)
 Color Temperature (CCT)
 Replacement
 Dimming Compatible
 Lumen Maintenance (L70)
CERTIFICATIONS

LED Omni-Directional A Lamps Non-Dimmable E26 Base



3000K options also available.

LED Omni-Directional High CRI A Lamps E26 Base



MODEL NUMBER	10A19DLED927/G4	10A19DLED930/G4
ORDER CODE	107605	107606
Input Wattage	10W	10W
Voltage	120V	120V
Delivered Lumens (lm)	800 lm	800 lm
Efficacy (lm/W)	80 lm/W	80 lm/W
Color Rendering Index (CRI)	90	90
Color Temperature (CCT)	2700K	3000K
Replacement	60W INC	60W INC
Dimming Compatible	Yes	Yes
Lumen Maintenance (L70)	25,000 hours	25,000 hours
CERTIFICATIONS	cULus, RoHS, ENERGY STAR®	cULus, RoHS, ENERGY STAR®

LED Omni-Directional JA8 Certified A19 Lamps E26 Base



MODEL NUMBER	10A19DLED927/JA8	10A19DLED930/JA8
ORDER CODE	107622	107623
Input Wattage	10W	10W
Voltage	120V	120V
Delivered Lumens (lm)	800 lm	800 lm
Efficacy (lm/W)	80 lm/W	80 lm/W
Color Rendering Index (CRI)	92	94
Color Temperature (CCT)	2700K	3000K
Replacement	60W INC	60W INC
Dimming Compatible	Yes	Yes
Lumen Maintenance (L70)	25,000 hours	25,000 hours
CERTIFICATIONS	cULus, RoHS, ENERGY STAR®, JA8	cULus, RoHS, ENERGY STAR®, JA8

LED Omni-Directional JA8 Certified A21 Lamps E26 Base



MODEL NUMBER	17A21DLED930/JA8
ORDER CODE	107851
Input Wattage	17W
Voltage	120V
Delivered Lumens (lm)	1600 lm
Efficacy (lm/W)	94 lm/W
Color Rendering Index (CRI)	90
Color Temperature (CCT)	2700K
Replacement	100W INC
Dimming Compatible	Yes
Lumen Maintenance (L70)	25,000 hours
CERTIFICATIONS	cULus, RoHS, ENERGY STAR®, JA8

LED Omni-Directional JA8 Certified, Enclosed Rated A Lamps E26 Base



MODEL NUMBER	E10A19DLED927/JA8	E10A19DLED930/JA8
ORDER CODE	107624	107625
Input Wattage	10W	10W
Voltage	120V	120V
Delivered Lumens (lm)	800 lm	800 lm
Efficacy (lm/W)	80 lm/W	80 lm/W
Color Rendering Index (CRI)	92	92
Color Temperature (CCT)	2700K	3000K
Replacement	60W INC	60W INC
Dimming Compatible	No	No
Lumen Maintenance (L70)	25,000 hours	25,000 hours
CERTIFICATIONS	cULus, RoHS, ENERGY STAR®, JA8	cULus, RoHS, ENERGY STAR®, JA8

E9A19DLED27/G2	
102169	MODEL NUMBER
9W	ORDER CODE
120V	Input Wattage
800 lm	Voltage
89 lm/W	Delivered Lumens (lm)
81	Efficacy (lm/W)
2700K	Color Rendering Index (CRI)
60W INC	Color Temperature (CCT)
Yes	Replacement
25,000 hours	Dimming Compatible
cULus, RoHS, ENERGY STAR®	Lumen Maintenance (L70)

3000K options also available.

CERTIFICATIONS

LED Omni-Directional Enclosed Rated A Lamps E26 Base



E9A19GUDLED27/G2	
102171	MODEL NUMBER
9W	ORDER CODE
120V	Input Wattage
800 lm	Voltage
89 lm/W	Delivered Lumens (lm)
81	Efficacy (lm/W)
2700K	Color Rendering Index (CRI)
60W INC	Color Temperature (CCT)
Yes	Replacement
25,000 hours	Dimming Compatible
cULus, RoHS, ENERGY STAR®	Lumen Maintenance (L70)

3000K options also available.

CERTIFICATIONS

LED Omni-Directional Enclosed Rated A Lamps GU24 Base



9BR30SDLED30	
101363	MODEL NUMBER
9W	ORDER CODE
120V	Input Wattage
650 lm	Voltage
72 lm/W	Delivered Lumens (lm)
85	Efficacy (lm/W)
3000K	Color Rendering Index (CRI)
65W INC	Color Temperature (CCT)
Yes, 3000K - 2200K	Replacement
25,000 hours	Dimming Compatible
cULus, ENERGY STAR®, FCC, RoHS	Lumen Maintenance (L70)

3000K options also available.

CERTIFICATIONS

LED Warm-On-Dim BR Lamps E26 Base



6P20DLED27FL	10P30DLED27FL	10P30LNDLED27FL	13P38DLED27FL	MODEL NUMBER
102174	102176	102178	102180	ORDER CODE
6W	10W	10W	13W	Input Wattage
120V	120V	120V	120V	Voltage
450 lm	750 lm	750 lm	950 lm	Delivered Lumens (lm)
75 lm/W	75 lm/W	75 lm/W	73 lm/W	Efficacy (lm/W)
≥80	≥80	≥80	≥80	Color Rendering Index (CRI)
2700K	2700K	2700K	2700K	Color Temperature (CCT)
50W INC	75W INC	75W INC	90W INC	Replacement
Yes	Yes	Yes	Yes	Dimming Compatible
25,000 hours	25,000 hours	25,000 hours	25,000 hours	Lumen Maintenance (L70)
cETL, RoHS ENERGY STAR®	cETL, RoHS ENERGY STAR®	cETL, RoHS ENERGY STAR®	cETL, RoHS ENERGY STAR®	CERTIFICATIONS

3000K & 4000K options also available. Flood 35° and Narrow Flood 25° beam angles available.

LED PAR Lamps E26 Base



LED Candelabra B11 Lamps E12 Base Single & Multi Packs



	Single	3 Pack	Bulk Pack
MODEL NUMBER	5B11DLED27/G2	5B11DLED27/G2/3P	5B11DLED27/G2/BP
ORDER CODE	107507	107508	107587
Input Wattage	5W	5W	5W
Voltage	120V	120V	120V
Delivered Lumens (lm)	325 lm	325 lm	325 lm
Efficacy (lm/W)	65 lm/W	65 lm/W	65 lm/W
Color Rendering Index (CRI)	80	80	80
Color Temperature (CCT)	2700K	2700K	2700K
Replacement	40W INC	40W INC	40W INC
Dimming Compatible	Yes	Yes	Yes
Lumen Maintenance (L70)	15,000 hours	15,000 hours	15,000 hours
CERTIFICATIONS	cULus, RoHS ENERGY STAR®	cULus, RoHS ENERGY STAR®	cULus, RoHS ENERGY STAR®

LED Globe Lamps E26 Base Single & Multi Packs



	Single	3 Pack	Bulk Pack
MODEL NUMBER	6G25DLED27/G2	6G25DLED27/G2/3P	6G25DLED27/G2/BP
ORDER CODE	107505	107506	107588
Input Wattage	6W	6W	6W
Voltage	120V	120V	120V
Delivered Lumens (lm)	450 lm	450 lm	450 lm
Efficacy (lm/W)	75 lm/W	75 lm/W	75 lm/W
Color Rendering Index (CRI)	80	80	80
Color Temperature (CCT)	2700K	2700K	2700K
Replacement	40W INC	40W INC	40W INC
Dimming Compatible	Yes	Yes	Yes
Lumen Maintenance (L70)	25,000 hours	25,000 hours	25,000 hours
CERTIFICATIONS	cULus, RoHS ENERGY STAR®	cULus, RoHS ENERGY STAR®	cULus, RoHS ENERGY STAR®

LED Omni-Directional A Lamps Non-Dimmable E26 Base Multi Packs



	4 Pack	4 Pack
MODEL NUMBER	9A19ND27/4P-180	9A19ND50/4P-149
ORDER CODE	107757	107759
Input Wattage	9.5W	9W
Voltage	120V	120V
Delivered Lumens (lm)	800 lm	800 lm
Efficacy (lm/W)	84 lm/W	84 lm/W
Color Rendering Index (CRI)	82	82
Color Temperature (CCT)	2700K	5000K
Replacement	60W INC	60W INC
Dimming Compatible	No	No
Lumen Maintenance (L70)	15,000 hours	15,000 hours
CERTIFICATIONS	cULus, RoHS, ENERGY STAR®	cULus, RoHS, ENERGY STAR®

LED Area Lamp E39 Base



	AR100LED50
MODEL NUMBER	AR100LED50
ORDER CODE	101497
Input Wattage	100W
Voltage	120-277V
Delivered Lumens (lm)	10,500 lm
Efficacy (lm/W)	100 lm/W
Color Rendering Index (CRI)	≥80
Color Temperature (CCT)	5000K
Replacement	400W MH
Dimming Compatible	No
Lumen Maintenance (L70)	50,000 hours
CERTIFICATIONS	cULus, DLC, RoHS

LED Direct Fit T8
Coated Glass

2' Tube	2' Tube
L9T8DF240-CG4	L9T8DF250-CG4
107769	107770
9W	9W
120-277V	120-277V
1350 lm	1400 lm
150 lm/W	155 lm/W
82	82
4000K	5000K
17W FLUOR	17W FLUOR
No	No
25,000 hours	25,000 hours
cULus, ETL Sanitation, RoHS, DLC	cULus, ETL Sanitation, RoHS, DLC

MODEL NUMBER
ORDER CODE
Input Wattage
Voltage
Delivered Lumens (lm)
Efficacy (lm/W)
Color Rendering Index (CRI)
Color Temperature (CCT)
Replacement
Dimming Compatible
Lumen Maintenance (L70)

CERTIFICATIONS



LED Direct Fit T8
Coated Glass

4' Tube	4' Tube	4' Tube
L13T8DF435-CG4	L13T8DF440-CG4	L13T8DF450-CG4
107221	107222	107223
13W	13W	13W
120-277V	120-277V	120-277V
1800 lm	1900 lm	2000 lm
110 lm/W	112 lm/W	115 lm/W
83	83	83
3500K	4000K	5000K
32W FLUOR	32W FLUOR	32W FLUOR
Yes	Yes	Yes
50,000 hours	50,000 hours	50,000 hours
cULus, ETL Sanitation, RoHS, DLC	cULus, ETL Sanitation, RoHS, DLC	cULus, ETL Sanitation, RoHS, DLC

MODEL NUMBER
ORDER CODE
Input Wattage
Voltage
Delivered Lumens (lm)
Efficacy (lm/W)
Color Rendering Index (CRI)
Color Temperature (CCT)
Replacement
Dimming Compatible
Lumen Maintenance (L70)

CERTIFICATIONS



LED Direct Fit T8
Plastic

4' Tube	4' Tube	4' Tube
L17T8DF435	L17T8DF440	L17T8DF450
107206	107207	107208
17W	17W	17W
120-277V	120-277V	120-277V
2200 lm	2200 lm	2200 lm
113 lm/W	113 lm/W	113 lm/W
84	84	84
3500K	4000K	5000K
32W FLUOR	32W FLUOR	32W FLUOR
No	No	No
50,000 hours	50,000 hours	50,000 hours
cETL, RoHS, DLC	cETLus, RoHS, DLC	cETLus, RoHS, DLC

MODEL NUMBER
ORDER CODE
Input Wattage
Voltage
Delivered Lumens (lm)
Efficacy (lm/W)
Color Rendering Index (CRI)
Color Temperature (CCT)
Replacement
Dimming Compatible
Lumen Maintenance (L70)

CERTIFICATIONS



LED Direct Fit T5
Coated Glass

4' Tube	4' Tube	4' Tube
L25T5DF435-CG4	L25T5DF440-CG4	L25T5DF450-CG4
107339	107340	107341
25W	25W	25W
120-277V	120-277V	120-277V
3200 lm	3200 lm	3200 lm
116 lm/W	112 lm/W	115 lm/W
83	83	83
3500K	4000K	5000K
54W T5HO	54W T5HO	54W T5HO
No	No	No
50,000 hours	50,000 hours	50,000 hours
cULus, ETL Sanitation, RoHS, DLC	cULus, ETL Sanitation, RoHS, DLC	cULus, ETL Sanitation, RoHS, DLC

MODEL NUMBER
ORDER CODE
Input Wattage
Voltage
Delivered Lumens (lm)
Efficacy (lm/W)
Color Rendering Index (CRI)
Color Temperature (CCT)
Replacement
Dimming Compatible
Lumen Maintenance (L70)

CERTIFICATIONS



LED Linear T8 Internal Driver Lamps Glass



	2' Tube	3' Tube	6' Tube
MODEL NUMBER	L9T8SE240-G*	L12T8SE340-G	L30T8SE640-G
ORDER CODE	101598	101600	101602
Input Wattage	9W	12W	30W
Voltage	120-277V	120-277V	120-277V
Delivered Lumens (lm)	1150 lm	1450 lm	3600 lm
Efficacy (lm/W)	127 lm/W	120 lm/W	120 lm/W
Color Rendering Index (CRI)	≥82	≥82	≥82
Color Temperature (CCT)	4000K	4000K	4000K
Replacement	17W FLUOR	32W FLUOR	70W FLUOR
Dimming Compatible	No	No	No
Lumen Maintenance (L70)	50,000 hours	50,000 hours	50,000 hours
CERTIFICATIONS	cULus, NSF, RoHS	cULus, NSF, RoHS	cULus, NSF, RoHS

*3500K & 5000K options also available. L9T8SE240-G is DLC Qualified.

LED T8 External Driver Plastic




	4' Tube	4' Tube	4' Tube
MODEL NUMBER	L19T8EX435	L19T8EX440	L19T8EX450
ORDER CODE	107289	107290	107291
Input Wattage	19W	19W	19W
Voltage	120-277V	120-277V	120-277V
Delivered Lumens (lm)	2350 lm	2350 lm	2350 lm
Efficacy (lm/W)	124 lm/W	124 lm/W	124 lm/W
Color Rendering Index (CRI)	82	82	82
Color Temperature (CCT)	3500K	4000K	5000K
Replacement	32W FLUOR	32W FLUOR	32W FLUOR
Dimming Compatible	No	No	No
Lumen Maintenance (L70)	50,000 hours	50,000 hours	50,000 hours
CERTIFICATIONS	cULus, RoHS, DLC, FCC	cULus, RoHS, DLC, FCC	cULus, RoHS, DLC, FCC

External Driver



	1 Lamp Driver	2 Lamp Driver	2 Lamp Driver	3 Lamp Driver
MODEL NUMBER	DR1L	DR2L	DR3L	DR4L
ORDER CODE	107292	107293	107294	107295
Input Voltage (V)	120-277V	120-277V	120-277V	120-277V
Input Frequency (Hz)	50/60 Hz	50/60 Hz	50/60 Hz	50/60 Hz
Max Input Power (W)	22W	44W	66W	88W
Min Power Factor (%)	0.87% (277Vac)	0.87% (277Vac)	0.87% (277Vac)	0.87% (277Vac)
Inrush Current	50Apk-pk	50Apk-pk	50Apk-pk	50Apk-pk
Output Channel	1	2	3	4
Max Output Voltage (V)	67V	67V	67V	67V
Max Output Current (mA)	310 x 1 mA	310 x 1 mA	310 x 1 mA	310 x 1 mA
CERTIFICATIONS	-	-	-	-

LED PL DirectFit Retrofit Lamps



	Horizontal	Vertical
MODEL NUMBER	11PLG24QHLED27	11PLG24QVLED27
ORDER CODE	100945	100948
Input Wattage	11W	11W
Voltage	120-277V	120-277V
Delivered Lumens (lm)	950 lm	950 lm
Efficacy (lm/W)	86 lm/W	86 lm/W
Color Rendering Index (CRI)	≥80	≥80
Color Temperature (CCT)	2700K	2700K
Replacement	26W CFL	26W CFL
Dimming Compatible	No	No
Lumen Maintenance (L70)	50,000 hours	50,000 hours
CERTIFICATIONS	rUL, RoHS	rUL, RoHS

3500K and 4000K options also available.

NOTE: Remaining stock of discontinued products may be available; contact your local sales representative for information. MaxLite will not create additional inventory for discontinued models.

Discontinued LED Indoor Fixtures						
Direct Lit Panels			3500K Eco-T		5000K ArcMax	Cooler Lights
MLFP14DE35XX			MLRT22D2535		MLVT14D4250	48RL18XX
MLFP22DE35XX			MLRT22D3535		MLVT22D3550	60RL20XX
MLFP24DE45XX			MLRT24D3535		MLVT22D35550/SB	72RL30XX
			MLRT24D4535		MLVT24D4250/SB	
DLR Downlights (4", 6", 8", and 9")			Residential Retrofits		Adjustable Retrofits	
DLR410XX	DLR630XX	DLR910XX	RR61430W		RR612XXWC-L4	RRA61030W
DLR415XX	DLR810XX	DLR915XX	RR61441W		RR618XXW-L4	RRA61041W
DLR420XX	DLR815XX	DLR920XX	RR61450W		RR619XXWC-L4	RRA610SSW
DLR610XX	DLR820XX	DLR930XX	RR411XXW-L4			
DLR615XX	DLR830XX	DLR950XX	RR412XXWC-L4			
DLR620XX	DLR850XX		RR612XXW-L4			
120-277V Residential Fixtures			Utility Wraps		Vapor Tights	Edge Lit Panels
RFR614ICATXXW			LSU2406SU30DVXX		LSV2406SU30DVXX	MLFP14EP36XX-215
RF614ICATXXW			LSU4806SU20DVXX		LSV4806SU30DVXX	MLFP22EP40XX
			LSU4806SU30DVXX		LSV4806SU50DVXX	MLFP24EP50XX
			LSU4806SU50DVXX			
Cooler Door Fixture			Baymax Highbay Linear		Shop Light	
36RDL30	48RDL41	60RDL50	BLHT150USD4815		BLHT150USD4815EM	LS-4848U-50
36RDL41	48RDL50	72RDL30	BLHT150USD4815C12		BLHT150USD4815EMMSV	
36RDL50	60RDL30	72RDL41	BLHT150USD4815C27		BLHT150USD4815MSO	
48RDL30	60RDL41	72RDL50	BLHT150USD4815EM		BLHT150USD4815MSV	

Discontinued LED Outdoor Fixtures			
Medium Area Lights	Medium Flood Lights	WallMax Small Wall Packs	Small Cutoff Wall Packs
MAL55XXXXXXXXXX	MFL55XXXXXXXXXX	WPS20AU50B	WPCS20AU50B
MAL80XXXXXXXXXX	MFL80XXXXXXXXXX		
MAL105XXXXXXXXXX	MFL105XXXXXXXXXX		
Adjustable Wall Packs	Post Tops	Canopies	High Output Flood Lights
SAW13	PTD80	PKGS45	ELLF135*
SAW26	PTD100	RC94	ELLF270*
LAW74			ELLF405*

*Excludes hazardous location models

Discontinued General Purpose LED Lamps				
A Lamps				
6A19DLED27/G2	15A21DLED27/G2	9A19GUDLED30/G2	11A19DLED30	12A19DLED41
6A19DLED30/G2	15A21DLED30/G2	9A19GUDLED40/G2	12A19DLED930	E9A19DLED27
9A19DLED40	6A19GUDLED27/G2	11A19GUDLED40/G2	12A19DLED27	E9A19DLED30
11A19DLED30/G2	9A19GUDLED27/G2	15A21GUDLED27/G2	12A19DLED30	E9A19GUDLED27
MR16 Lamps		PL Lamps		Baymax High/Low Bay Retrofit Lamp
7MR16GUDLED30FL		13PLG24QHLED35		BLHR43UN27B
		13PLG24QHLED41		BLHR43UN50B
PAR Lamps		Linear T8 Lamps		
12P30DLED27NF		L10T8SE235	L10T8SE250	
12P30LNDLED27FL/G2		L10T8SE241	L10T8SE341	
15P38DLED27FL/G2				

MAKE YOUR

These Point-of-Purchase and other sales tools are available through our stocking programs and upon request.



LED Lamp Test Case

2015LEDCASE



Green - Outdoor Fixture Bag

LGGREENDUFFEL



Green - 2x2 Flat Panel Fixture Bag

GREENECOTCASE



Green - Linear Fixture Bag

GREENLINEARCASE



QuadroMAX® Carrying Case

QUADROMAXCASE



QuadroMAX® 2016 Brochure

QUADROMAX-BRO-16



MaxLite Magnetic Counter Mat

COUNTERMAT




QuadroMAX® Insert for Counter Mat

QUADROMAXINSERT



LED General Catalog

LEDGENCATQ316



Light Sources Catalog



LED New Product Supplement Catalog

2016NEWPRODSUP



3-Ring Binder

BINDER



LED Lighting Solutions Brochures



MaxLite Logo Barstool Cover

BARSTOOLCOVER



Ask About MaxLite Branded Give Aways

SALES POP!



Gondola Rack
GONDOLA



Cardboard Floor Display Stand
BULB PROMO STAND



MaxLite Authorized Dealer Window Cling



LED T8 Floor Display
LEDT8DISPLAY



2-Socket Lamp Demo Display Bar
LAMP SOCKET DISPLAY



4-Socket PL Lamp Display Bar
PLDISPLAY4SOCKET



LED Flood Light Counter Top Display
SKRFLDDISP




LED Small Adjustable Wall Pack Counter Top Display
LEDSAWDISPLAY



40W LED Wall Pack Counter Top Display
WALLPACKDISP



40W LED Dark Sky Counter Top Display
MLLWP40LED50SDISP



40W LED Canopy Counter Top Display
MLGAR40LED50DISP



LED Lightbar Counter Top Display
MLSDLBDISP



LED Faux Can Counter Top Display
LEDFAUXCANDISPLAY



6" LED Retrofit Counter Top Display
RR61430WDISP



6" Warm-on-Dim LED Adjustable Retrofit Counter Top Display
WARMONDIMDISP



MaxLite 2'x4' Authorized Dealer Vinyl Banner
MAXLITEDEALERBANNER

Find, like and follow us on social media.




MaxLite®

A NEW WAVE OF LIGHT

www.maxlite.com



Item # 2016NEWPRODSUP
Ord. Code: 107762



7 67627 35803 6

Corporate Headquarters

12 York Ave.
West Caldwell, NJ 07006
T: 1-800-555-5629
F: 973-244-7333

California Facility

1148 North Ocean Circle
Anaheim, CA 92806
T: 1-800-793-1212
F: 714-678-5096