


# OUTDOOR






# LED INDOOR LIGHTING











#### ASD Lighting Corp.

ASD Lighting Corp started in Eastern Europe in 1999. Since that time, ASD has grown to become one of the largest lighting manufacturers in Eastern Europe with thousands of SKU's.

ASD opened in the US market in 2014 in Canton, MA and is one of the fastest growing LED luminaire manufacturers in the country. We produce high quality LED fixtures at aggressive prices making us the best value for the money in the market.

We have a massive amount of in-stock inventory in our 100,000 sq ft. warehouse in Massachusetts eliminating any lead time.

We offer fast reliable shipping and will ship orders the same day whenever possible.

We are the "New Standard in Lighting". We develop reliable quality fixtures with new energy saving technologies at affordable pricing.

ASD Lighting is 100% committed to the satisfaction of our customers and never stop improving.





#### Certification \_\_\_\_\_

Our products are designed and engineered in Europe.

Our product development laboratory and skilled technical staff allow us to completely control the manufacturing process to produce high-quality, reliable lighting fixtures.

Our fixtures are put through rigorous testing to receive UL, ETL and FCC certification as well as DLC and Energy Star ratings.



#### LED Edge-Lit Flat Panel

ASD Edge-Lit Flat Panels are the best choice for all recessed, suspended and surface mounted applications. Our panels are cULus and DLC approved\*. Available in DLC Standard and DLC Premium, these contemporary panels are only 1/2 " thick making them one of the slimmest panels on the market. Up to 20 dimmable panels can be linked to each master panel. Hanging sets, surface mount kits and sheetrock kit options are available for a variety of installation options.


- Available in 1x4, 2x2 and 2x4 sizes •
- High Efficiency DLC Standard and DLC Premium •
- Recessed, suspended and surface mounting options Premium 139,000 hour L70 lifetime •
- Standard 0-10 V dimming

- 5-year limited warranty
- Standard 81,000 hour L70 lifetime

asd

O FC

\*Please check with DLC to determine your local rebate incentives based on DLC fixture rating



rannity	JIZE	Diffifiable	Walls	CCT	JEITES
ASD-ELP		D			
Edge-Lit Panel	14 = type 1x4		22 = 22 W	<b>35</b> = 3,500 K	HE
	22 = type 2x2		<b>27</b> = 27 W	<mark>40</mark> = 4,000 K	STD
	<b>24</b> = type 2x4		<b>36</b> = 36 W	<mark>50</mark> = 5,000 K	PRM
			<b>40</b> = 40 W	<mark>65</mark> = 6,500 K	
			<b>60</b> = 60 W		

#### LED Direct-Lit Panel


ASD Direct-Lit Panels are a great economical choice for an easy direct replacement for recessed panel lighting. They are sold in pairs and are cULus listed and DLC approved\*. Once installed, these panels have the look of a standard fluorescent fixture with a prismatic lens, but are only 1" thick. Our panels are reasonably priced, maintenance free and can significantly reduce your energy bills. Up to 20 dimmable panels can be linked to each master panel.

- Available in 2x2 and 2x4 sizes
- Standard 0-10 V dimming
- Greater than 100,000 hour L70 lifetime

\*Please check with DLC to determine your local rebate incentives based on DLC fixture rating







2.8"

1"

			a case			'		
90	lm/w							
2x2	ASD-DLP22D4040	40	4,000	3,761	2	3.0	80W	FL
2x2	ASD-DLP22D4050	40	5,000	3,707	2	3.0	80W	FL
2x4	ASD-DLP24D6040	60	4,000	5,310	2	3.0	120W	FL
2x4	ASD-DLP24D6050	60	5,000	5,492	2	3.0	120W	FL

ССТ

Watts

11	0	lm/	w
_	<u> </u>		

Model

2x2	ASD-DLP22D2735HE	27	3,500	3,240	2	4.2 Standard	65W FL
2x2	ASD-DLP22D2740HE	27	4,000	3,385	2	4.2 Standard	65W FL
2x2	ASD-DLP22D2750HE	27	5,000	3,420	2	4.2 Standard	65W FL
2x4	ASD-DLP24D4035HE	40	3,500	4,240	2	4.2 Standard	98W FL
2x4	ASD-DLP24D4040HE	40	4,000	4,320	2	4.2 Standard	98W FL

Family	Size	Dimmable	Watts	CCT	Series
ASD-DLP		D			HE
Direct-Lit Panel	22 = type 2x2		22 = 22 W	<b>35</b> = 3,500 K	
	<b>24</b> = type 2x4		<b>27</b> = 27 W	<b>40</b> = 4,000 K	
			<b>40</b> = 40 W	<b>50</b> = 5,000 K	
			<mark>60</mark> = 60 W		

Recessed mounting

5-year limited warranty


Type

#### LED Driver with a Mounting Box

Engineered for a long life of high performance, our drivers are a vital component to our panels. ASD drivers come with a quick disconnect plug (85and 110lm/w models) and all have 0-10v dimming. This product comes with a 5-year warranty.



	Model	Power	Input Voltage	Output Voltage	Max Current	Product Code	Pcs in one carton
 4.1°	ASD-BLP22D ASD-BLP27D ASD-BLP40D ASD-BLP60D	22 W 27 W 40 W 60 W	100-277 V 100-277 V 100-277 V 100-277 V	30-42 V 30-42 V 30-42 V 30-42 V 30-42 V	500 mA 700 mA 1,050 mA 1,500 mA	027.0104 027.0103 027.0101 027.0102	4 4 4 4





Pcs in

DLC

Equivalency

Lm

#### Accessories for LED Edge-Lit Flat Panels

#### FRAME FOR SURFACE MOUNTING


only for LED Edge-Lit Flat Panels


LED panels are easily mounted on horizontal or sloped surfaces with our surface mount frame.

Model	Dimensions	Pcs in a case
ASD-FELP14	48" x 12" x 2.4"	9
ASD-FELP22	24" x 24" x 2.4"	9
ASD-FELP24	48" x 24" x 2.4"	9

Family	Size
ASD-FELP	
Frame for Edge-Lit Panel	<b>14</b> = type 1x4
	22 = type 2x2
	24 = type 2x4







#### FRAME FOR RECESSED SHEETROCK MOUNT

for LED Edge-Lit and Direct-Lit Panels

Allows for flush mounting into a sheetrock ceiling.

Model	Dimensions	Pcs in a case		
ASD-FDW-ELP14	47 1/2" x 11 3/8" x 1"	20		
ASD-FDW-ELP22	25 1/4" x 25 1/4" x 1"	20		
ASD-FDW-ELP24	49 1/4" x 25 1/4" x 1"	20		

Family	Size				
ASD-FDW-ELP					
Frame for Dry Wall	14 = type 1x4				
	22 = type 2x2				
	24 = type 2x4				


#### HANGING SET

only for 2x2 and 1x4 LED Edge-Lit Flat Panels

This kit contains four suspension wires, anchors and screws. You will be able to adjust the length of the suspension wires to your desired fixture height allowing you to hang from flat or sloped ceilings.

Model	Dimensions (L)	Pcs in a case			
ASD-CHS4	4"	50			
ASD-CHS6	6"	50			





Dimensions

**4** = 4" **6** = 6"

Family

Ceiling Hanging set

ASD-CHS



#### LED SMD Floodlight

The ASD DLC 3.0 approved and UL listed LED SMD Floodlights are the best choice for all floodlight applications. Brightly illuminate walkways, parking areas, building entrances and more. Durable high quality and performance in an affordable price range.

- Resistant to high and low temperatures
- Operating temperature -40-122°F (-40-50°C)
- Suitable for wet locations, degree of protection
- High performance Advanced SMD technology
- 5-year limited warranty >50,000 Hrs •
- Low energy consumption

\*Please check with DLC to determine your local rebate incentives based on DLC fixture rating



				Model	Watts	CCT	Lm	Pcs in a case	DLC	Equivalency
	E C C C C C C C C C C C C C C C C C C C	211/8" .2/1 2 .2/1 2	53/16"    	ASD-SFL2040 ASD-SFL2050 ASD-SFL3040 ASD-SFL3050	20 20 30 30	4,000 5,000 4,000 5,000	1,560 1,615 2,365 2,441	4 4 4 4	3.0 3.0 3.0 3.0 3.0	70W MH 70W MH 100W MH 100W MH
	E E E E E	87/8" "7/L	6 1/8" 	ASD-SFL5040 ASD-SFL5050	50 50	4,000 5,000	3,880 4,123	4 4	3.0 3.0	180W MH 180W MH
	EFE FC	11 1/4" "7/L	63/4*	ASD-SFL7540 ASD-SFL7550 ASD-SFL10040 ASD-SFL10050	75 75 100 100	4,000 5,000 4,000 5,000	6,084 6,420 7,783 8,304	4 4 4 4	3.0 3.0 3.0 3.0	270W MH 270W MH 350W MH 350W MH
	Ese FC	11 7/16° •91/6 71	6 11/16°	ASD-SFL15040 ASD-SFL15050 Family	150 150	4,000 5,000	11,343 11,927 Watte	4 4	3.0 3.0	540W MH 540W MH CCT
<u> </u>			╟─┳	ASD-SFL LED SMD Floodli	ght		= 20 W; 30 = 50 W; 75	) = 30 W		50 = 5,000 K
							= 50 W; 73 100 W; 15		I	

P66

#### Model Dimensions Pcs in a case POLE MOUNTING BRACKET Our Pole mount bracket allows you to easily attach ASD-PMB-FL 7.9"x3.2"x3.5" 20 our LED SMD Floodlights to our adapter bracket for pole mount applications.

### LED SMD Compact Floodlight with knuckle \_

Our UL and DLC 4.2 Compact Flat floodlights measure around 1 inch thick making it one of the thinnest, vet durable floodlights on the market today. Using LED SMD advanced technology, our floods will outperform most others with ease. These are perfect for commercial and residential applications and easy to install with the adjustable knuckle mount. They are a top choice for illuminating driveways, parking lots, buildings, entryways and signs.

- Resistant to high and low temperatures; operating temperature -4-104°F (-40-40°C) • 5-year limited warranty - >36,000 Hrs
- Suitable for wet locations IP 65
- High performance Advanced SMD technology
- Low energy consumption

e abaal with DLC to determine your least rebate incentives based on DLC future ratios



2990.

Please check with DLU to deter	mine your local rebi	ate incentives based on DLL fixture rating						
	CUL US	5 3/8" 1 1/8"	Model	Watts	ССТ	Lm	DLC	Equivalency
	FC FC	912/16	ASD-CSFL-A1050	10	5,000	1,029	4.2	35W MH
		7 1/2" 1 3/8"	ASD-CSFL-A2050	20	5,000	1,865	4.2	75W MH
Ţ		81/2	ASD-CSFL-A3050 ASD-CSFL-A5050	30 50	5,000 5,000	2,877 4,872	4.2 4.2	100W MH 180W MH
	۵. س	9 5/16" 1 5/8"	Family			Watts		CCT
100 March 100	CUS		ASD-CSFL					
	FC		LED SMD COMPA Floodlight	ACT	10 = 10 W; 20 = 20 W 30 = 30 W; 50 = 50 W			<b>50</b> = 5,000 K


#### LED SMD Bullet Floodlight with knuckle \_

ASD LED SMD Bullet Flood lights uses the latest in solid state lighting technology for high efficiency, long life and low maintenance. This fixture is perfect for facade, landscape and sign lighting applications. Sealed to keep out dirt, bugs and moisture, the Bullet Floods are constructed with a precision die-cast aluminum housing and tempered, shatter-resistant glass for a sleek appearance and maximum durability.

- Resistant to high and low temperatures; operating temperature -40-104°F (-40-40°C) • 5-year limited warranty - >54,000 Hrs
- ½" NPS threaded locking swivel arm

NEW

Suitable for wet locations IP 65 •



LED SMD Wallpack

ASD LED Wall Packs feature leading-edge optics that increase light output and reduce shadows to create safe, brightly-lit outdoor environments in parking garages, entrances, schools, hospitals, hotels, public areas and outdoor walkways. There is an optional Glare Shield available for dark sky compliance. The shield will help to minimize blue light emissions and light the area that needs it.

- Operating temperature -40-104°F (-40-40°C) Greater than 54,000 hour •
- Standard 0-10V dimming (80W model only) •
- Suitable for wet locations IP 65 •
- Durable borosilicate prismatic glass lens •
- LED lifetime
- 5-year warranty
- Low energy consumption



Dimensions

12 13/16"x9 1/2"x10 1/8"

Prs in a case

8



#### **GLARE SHIELD AVAILABLE (OPTIONAL)**

Optional shield will help to minimize blue light emissions and light the area that needs it.



#### LED COB Cutoff Wallpack

Our slim LED wallpacks are designed to replace up to a 400w metal halide producing an abundance of light with a fraction of the power. These durable low profile fixtures are great in a downlight or uplight application and are easily installable. Reduce shadows to create safe, brightly lit exterior environments for commercial buildings, schools, hospitals, hotels and more.

- Resistant to high and low temperatures; operating temperature -40-104°F (-40-40°C)
- 5-year limited warranty
- Low energy consumption
- Suitable for wet locations, degree of • protection IP 65
- Greater than 36,000 hour LED lifetime

Model

ASD-SWLP01-50/80

IP65

Prs in Model Watts CCT DLC Equivalency Lm a case 6 5/8 7 7/8' ASD-WLP02-30N50 30 5.000 2.716 8 4.2 Standard 100W MH 0 FC ASD-WLP02-50N50 50 5,000 4,542 8 4.2 Standard 150W MH 11 9/16' 91/2 (ዚ) 7,044 ASD-WLP02-75N50 5,000 4.2 Standard 250W MH 75 4 ASD-WLP02-100N50 100 5,000 10,277 4 4.2 Standard 2\*150W MH FC C Modification Watts Non-dimmable CCT Family ASD-WLP LED Wallpack 30 = 30 W: 50 = 50 W **50** = 5.000 K 75 = 75 W; 100 = 100 W

#### LED SMD Adjustable Cutoff Wallpack

Our LED SMD adjustable wall packs feature a hinged bracket to allow for simple beam angle adjustment. They are designed to replace up to a 400w metal halide producing an abundance of light with a fraction of the power. These low profile durable fixtures are great for a downlight or uplight and are easily installable. This is an ideal commercial outdoor fixture for buildings, parking garages, schools, and warehouses, is suitable for wet locations and harsh environments.

- Fixture head pivots fully up to 90°
- Suitable for wet locations, degree of protection IP 65
- Operating temperature -40-104°F (-40-40°C)
- Standard 0-10V dimming (80W and 120W models only)
- 5-year limited warranty
- Greater than 54,000 hour LED lifetime

LED ADJUST

50. 5000. 5387.

P65

**IP65** 


		5"	6"	Model	Watts	CCT	Lm	Pcs in a case	DLC	Equivalency
-		32/5		ASD-WLP02A-12N50B	12	5,000	1,321	12	4.2 Standard	70W MH
	C USTED USTED		11"	ASD-WLP02A-30N50B ASD-WLP02A-50N50B	30 50	5,000 5,000	3,298 5,287	4 4	4.2 Standard 4.2 Standard	150W MH 175W MH
			13"	ASD-WLP02A-80D50B ASD-WLP02A-120D50B	80 120	5,000 5,000	9,241 14,227	2 2	4.2 Standard 4.2 Standard	2*150W MH 400W MH
E 1		M 110 11	14	1	D:				COT	

Family	Modification	Watts	Dimmable	CCT
ASD-WLP	02A		N	
LED Adjustable Cutoff Wallpack		<b>12</b> = 12 W; <b>30</b> = 30 W; <b>50</b> = 50 W <b>80</b> = 80 W; <b>120</b> = 120 W	N = Non-dimmable	<b>50</b> = 5,000 K

#### LED SMD Full Cutoff Wallpack

ASD Full Cutoff Wallpacks offer controlled light output for general-purpose area and security lighting and are Dark-sky compliant. They are made with a die-cast aluminum housing and dark bronze finish. Our Full Cutoff LED wall pack is a perfect replacement for traditional outdoor wall packs.

- Fixture is full cutoff version (no uplight)
- Impact-resistant polycarbonate optical lens
- Operating temperature -40-104°F (-40-40°C)
- Standard 0-10V dimming (80W model only)
- Suitable for wet locations, degree of protection IP 65
- 5-year limited warranty
- Greater than 54,000 hour LED lifetime




#### LED Security Wallpack

ASD LED SMD Security Wallpacks with integrated dusk to dawn photocell sensor provide optimal illumination for commercial and industrial environments. This fixture is ideal for outdoor applications such as doorways, loading areas, walkways, post mounted applications and more.

- Tough polycarbonate lens for increased vandal resistance
- Advanced LED SMD technology •
- Built in photocell for dusk to dawn timing Greater than 54,000 hour LED lifetime •
- Operating temperature -40-104°F (-40-40°C)

NEW

- Suitable for wet locations IP 65
- 5-year limited warranty



### LED Area and Roadway Lighting

ASD LED Area and Roadway Lighting with dusk to dawn photocell offers security and safety and can be mounted to buildings or posts to fully illuminate areas such as doorways, garages, sheds, barns, driveways and more.

- Twist-lock photocell included
- Mounts directly or with • mounting arm (included)
- Durable Die-Cast Aluminum Housing
- Suitable for wet locations IP 65
- Operating temperature -40-104°F (-40-40°C)
- 5-year limited warranty
- Greater than 54,000 hour LED lifetime



1000. 2740.

IP65

- -


_	_	9 1/2*	Model	Watts CCT	Lm	Pcs in a case	DEL.	Equivalency
			ASD-ARL-50N50-PC	50 5,000	) 5,32	6 1	4.2 Standard	175W MH
Family ASD-ARL	Watts	Dimmable	C	CT			Photocell PC	
LED Area and Roadway light	<mark>50</mark> = 50 W	Non-dimmable	50 =	5,000 K			10	

LED Area and Roadway light

#### LED SMD Canopy .

ASD LED Canopy Lights are wet location rated and designed to withstand the elements while producing a substantial amount of light. This is an ideal replacement for an old, energy wasting halogen. Our Canopy is equipped with Advanced SMD technology for superior light output. There are no costly bulbs to change, virtually eliminating maintenance for years to come.

- Available in 30W, 50W and 75W
- High efficiency 105 lm/W
- Greater than 36,000 hour LED lifetime
- 5-year limited warranty
- Resistant to high and low
  temperatures
- Operating temperature -40-104°F (-40-40°C)
- Black or white finish



Family	Modification	Watts	Non-dimmable	CCT	Finish
ASD-CAN	01		N		
LED Canopy		<b>30</b> = 30 W; <b>50</b> = 50 W <b>75</b> = 75 W		<b>50</b> = 5,000 K	Black; $W =$ White

### LED SMD UFO HIGH BAY - WET LOCATION

Our New UFO style round high bay is the latest in LED technology. Smaller, more efficient, and longer lasting, our new IP65 – WET location rated LED UFO high bay fixture is at 130lm/w achieving desired light levels while using less power per fixture than most other LED High bay fixtures.

Light can be dimmed to ideal brightness levels to save energy and achieve the exact light level needed for your application.

- Available in 100W, 150W and 200W
- High efficiency 130 lm/W and up
- Greater than 54,000 hour L70 lifetime
- 5-year limited warranty
- Resistant to high and low temperatures; operating temperature -20-113°F (-30-45°C)



**IP65** 

	12 5/8"	Model	Watts	CCT	Lm	Pcs in a case	DEC	Equivalency
Constant Con	125/8. 21/14	ASD-UHB1-100D50PRM ASD-UHB1-150D50PRM ASD-UHB1-200D50PRM	100 150 200	5,000 5,000 5,000	13,519 20,401 26,895	1 1 1	4.2 Premium 4.2 Premium 4.2 Premium	400W MH 2*250W MH 600W MH

Family	Modification	Watts	Dimmable	ССТ	Series
ASD-UHB			D		PRM
LED UFO High Bay		100 = 100 W; 150 = 150 W		<b>50</b> = 5,000 K	Premium
		<b>200</b> = 200 W			

### LED SMD UFO HIGH BAY with J-Box

Our LED SMD cutting edge UFO High Bay is smaller, long lasting and extremely efficient. Less than 13 inches in diameter, this compact fixture really delivers high performance without sacrificing quality. The UHB5 series delivers efficient, uniform, high lumen output for high bay and low bay applications in industrial, commercial and retail environments. Included is an optional 3 in 1 dimming function (0-10vdc, PWM signal or resistance) to dim to desired light levels. Our innovative design with steel junction box on top of the fixture has two 1/2 " knockouts and two ¾ " knockouts and makes installation fast and simple with hook and pendant mount options.



- Available in 100W, 150W and 200W
- High efficiency 130 lm/W and up
- 100-277V and 480V options
- 5-year limited warranty
- Operating temperature -20-113°F (-30-45°C)

		12 5/8"	Model	Watts	CCT	Lm	Pcs in a case	ULL	Equivalency
			ASD-UHB5-100D50PRM ASD-UHB5-150D50PRM ASD-UHB5-200D50PRM ASD-UHB5HV-200D50PRM	100 150 200 200	5,000 5,000 5,000 5,000	13,460 19,902 26,499 28,134	1 1	4.2 Premium 4.2 Premium 4.2 Premium 4.2 Premium	400W MH 2*250W MH 600W MH 600W MH
Family	Modification	Watts	Din	nmable		С	CT	S	eries
ASD-UHB				D					PRM
LED UFO High Bay	5 5HV = High Voltage	<b>100</b> = 100 W; <b>150</b> = <b>200</b> = 200 W				<b>50</b> = !	5,000 K	Pre	emium

#### Accessories for UFO High Bay and UFO High Bay with j-box

UFO High Bay optional accessories are available to customize the fixture to your needs. These options include an inline wire connector for power cable, a polycarbonate diffuser and a polycarbonate bottom conical lens or aluminum diffuser.

 Female Male	Model	Materials	Pcs in a case
	LLT-M19CS03	Aluminum	1000
ASD-DUHB-16-90PC ASD-DUHB-19-90PC	ASD-DUHB-16-90PC ASD-DUHB-19-90PC	Polycarbonate Polycarbonate	10 10
ASD-BLUHB-16PC ASD-BLUHB-19PC	ASD-BLUHB-16PC ASD-BLUHB-19PC	Polycarbonate Polycarbonate	20 10
ASD-DUHB-16-90AL ASD-DUHB-21-90AL = $=$ $=$ $=$ $=$ $=$ $=$ $=$ $=$ $=$	ASD-DUHB-16-90AL ASD-DUHB-21-120ALG	Aluminum Aluminum	10 10

### Round High Bay \_

The ASD Series LED Round High Bay provides high performance at very affordable pricing eliminating the need for outdated, energy wasting high bay luminaires. Perfect for gymnasiums, warehouses, industrial facilities and other commercial high bay applications, our unique lightweight aluminum alloy design with loop heat pipe allows for excellent heat dissipation. The luminaire is made with an dimmable driver for excellent stability, high performance and long life.

- Available in 100W, 150W and 200W
- High efficiency 120 lm/W
- Greater than 68,000 hour L70 lifetime
- 5-year limited warrantyResistant to high and low temperatures;
- operating temperature -4-131°F (-20-55°C)

0	س	10 3/4"	. 8 1/4" .	Ma	del	Watts	CCT	Lm	Pcs in a case	DLC	Equivalency
	E STED USTED FC				1-100D35HE 1-100D50HE	100 100	3,500 5,000	11,603 11,940	4 4	4.2 Standard 4.2 Standard	250W MH 250W MH
÷	CUS USTED US FC	10 3/4"	91/4-		1-150D35HE 1-150D50HE	150 150	3,500 5,000	17,729 18,258		4.2 Standard 4.2 Standard	1*400W MH 1*400W MH
<u></u>	CUSUS USTED SEC FC	10 3/4*		ASD-LRHB	1-200D50HE	200	5,000	24,756	2	4.2 Standard	2 * 250W MH
Family		Modification	Watts		D	immab	le		ССТ		Series
ASD-LRHB LED Round High Bay		1	100 = 100 W; 150 = 200 = 200 W			D			8 <b>5</b> = 3,50 6 <b>0</b> = 5,00		HE

#### Accessories for Round High Bay

Round High Bay optional accessories are available to customize the fixture to your needs. These options include a polycarbonate diffuser and a polycarbonate bottom conical lens or aluminum diffuser.


-			Model	Materials	Pcs in a case
	16 3/4"		ASD-DRHB-16AL	Aluminum	10
	ASD-DRHB-16PC	ASD-DRHB-19PC			
	/2	<b>5</b>	ASD-DRHB-16PC	Polycarbonate	10
	/  → 16 1/8″	/	ASD-DRHB-19PC	Polycarbonate	10
	ASD-BLRHB-16PC	ASD-BLRHB-19PC			
	. <u>11/4</u> "	<u> </u>	ASD-BLRHB-16PC ASD-BLRHB-19PC	,	10 10

#### Linear High Bay \_

ASD Linear High bays are the perfect replacement for T5/T8 /T12 florescent and are capable of replacing up to 500w MH with only 180w. Our LED High-Bay fixtures are maintenance free and meet the harsh performance requirements of commercial and industrial environments with high quality, high efficiency and high lumen output to save you money. They are UL, DLC and motion sensor and DALI LED compatible.


• Up to 24,000 Lumens

- Standard 0-10 V dimming
- High efficiency 130 lm/W
- 5-year limited warranty
- Resistant to high and low temperatures; operating temperature -4-131°F (-20-55°C)
- Greater than 139,000 hour L70 lifetime



#### Accessories for Linear High Bay

ASD Lighting offers optional accessories for our warehouse high bay fixtures making them suitable for most applications. These accessories include a lens consisting of a PS prismatic cover and an iron frame, and a wire guard made of steel wire with metal clips for attachment.




#### LED Vaporproof Fixture

ASD Vapor Proof fixtures are the logical choice for harsh applications such as car washes, garages, stairwells, commercial kitchens, walk-in coolers, etc. These are IP66 rated making them dustproof and ideal for wet locations. Our Vapor proof fixtures are made from a polycarbonate housing and never lose their luster.

• Available in 4ft size

•

- Resistant to high and low temperatures; operating temperature -4-104°F (-20-40°C)
- High efficiency 110 lm/W
- Suitable for wet locations – IP66 rated
- 5-year limited warranty
- Greater than 83,000 hour L70 lifetime



40 = 4,000 K 50 = 5.000 K WET

LOCATIONS

WET

LOCATIONS

**IP66** 

**50** = 5,000 K

P66

#### Seamless LED Vaporproof Fixture

Our cutting edge Seamless Vapors are a contemporary version of the typical vapor proof fixture. This sleek new seamless design has a one piece body eliminating the need for clips. It has 4 gasketed screws and a gasketed end cap on both sides for easy connection. The body is polycarbonate, not plastic making this extremely durable and able to withstand water, dust, chemicals and maintain its color and luster. We have 110lm/w Standard non-dimmable and a new 125lm/w Premium 0-10v dimmable.

- Available in 4 ft and 8 ft sizes
- Resistant to high and low temperatures;
   operating temperature -4-104°F (-20-40°C)
- Suitable for wet locations IP66 rated
- 110 lm/W Standard and 125 lm/W Premium

Vandal Proof

5-year limited warranty, greater than 139,000 hour L70 lifetime

					Туре	Model	Watts	CCT	Lm	Peo in a case	DLC	Equivalency
				© <u>†</u> 3 1/8"	4 ft	ASD-LVP2SM-4N3135HE	31	3,500	3,425	9	4.2 Standard	76W FL
			48 1/16"	3 1/2"	4 ft	ASD-LVP2SM-4N3140HE	31	4,000	3,450	9	4.2 Standard	76W FL
	D.	<u>i</u>	40 1/10	31/2	4 ft	ASD-LVP2SM-4N3150HE	31	5,000	3,505	9	4.2 Standard	76W FL
×	F	2			4 ft	ASD-LVP2SM-4D3140PRM	31	4,000	3,861	9	4.2 Premium	90W FL
Afeet		9			4 ft	ASD-LVP2SM-4D3150PRM	31	5,000	3,860	9	4.2 Premium	90W FL
				;©†3 1/8"	8 ft	ASD-LVP2SM-8N6035HE	60	3,500	6,904	4	4.2 Standard	148W FL
		Us		+ <b>-</b> +	8 ft	ASD-LVP2SM-8N6040HE	60	4,000	6,960	4	4.2 Standard	
	LISI	ED		3 1/2"	8 ft	ASD-LVP2SM-8N6050HE	60	5,000	7,020	4	4.2 Standard	148W FI
×	Q				8 ft	ASD-LVP2SM-8D6040PRM		4,000	7,721		4.2 Premium	
8 feet	F	C	94 1/2"		8 ft	ASD-LVP2SM-8D6050PRM	60	5,000	7,721	4	4.2 Premium	175W FI
Family	Modification	Туре	Lens	Size		Dimmable	Watts		С	СТ	S	eries
ASD-LVP	2	S										
LED VaporProof		Seamless	M = Translucent	<mark>4</mark> = 4 ft	N	🛚 = Non-dimmable 🛛 🕄	1 = 31 V	N	<b>35</b> = 3	3,500 K		HE
			white Lens	<mark>8</mark> = 8 ft		D = Dimmable	<b>0</b> = 60 \	N	<b>40</b> = 4	4,000 K		PRM

#### LED Striplight Fixture

Our High performance, 0-10v dimmable one lamp and two lamp fixtures have the standard look of a strip light but with a contemporary flair. These low profile fixtures are able to be linked together for a seamless look with our included quick-connect to reduce installation time significantly. ASD LED Striplights have a strong polycarbonate lens, are maintenance free and will significantly reduce energy consumption.

• Available in 2 ft and 4 ft lengths

Low profile design

•

Operating temperature -4-113°F (-20-45°C)

5-year warrantyGreater than 100,000 hour

L70 lifetime

umption.

				Туре	Model	Watts	CCT	Lm	Pcs in a case	ULL	Equivalenc
				2 ft	ASD-LSF-2D1040	10	4,000	1,100	6	4.2 Standard	
		2 <u>3/16</u> " [2]	24"	2 ft	ASD-LSF-2D2040	20	4,000	2,200	6	4.2 Standard	51W FL
		2 <u>3/16</u> ° .:	40"	4 ft	ASD-LSF-4D4040	40	4,000	4,400	6	4.2 Standard	96W FI
Family		Size	Dimmable			Watts	6			ССТ	
ASD-LSF			D								

ASD-LSF		D		
LED Striplight fixture	<b>2</b> = 2 ft; <b>4</b> = 4 ft		<b>10</b> = 10 W; <b>20</b> = 20 W; <b>40</b> = 40 W	<b>40</b> = 4,000 K

#### LED Striplight Fixture Premium Series

ASD LED Strip lights are the perfect replacement for a fluorescent fixture. These fixtures are pendant or surface mounted and practically eliminate maintenance, as there are no costly bulbs to change. Perfect for task lighting, workshops, retail stores, coves, storage, display cases and more, they are available in 4' lengths and are able to quickly and easily be linked together for a seamless look.

- Available in 4 ft length
- Multiple fixtures may be linked together
- Fixture may be pendant, or surface mounted
- 5-year warranty
- Greater than 54,000 hour L70 lifetime



A	)		Туре	Model	Watts	CCT	Lm	Pcs in a case	DEL.	Equivalency
		48"		ASD-LSF2-4D2440PRM ASD-LSF2-4D4040PRM	24 40	4,000 4,000	3,152 5,205	4 4	4.2 Premium 4.2 Premium	
Family	Family Modification Size Dimmal		Dimmable	Watts		C	CT		Serie	es
ASD-LSF	2		D						PR	М
LED Striplight fixture		<b>4</b> = 4 ft		<b>24</b> = 24 W; <b>40</b> = 40 W		<b>40</b> = 4	,000 K		Premi	um


### LED Shoplight Fixture

ASD LED Shoplight Fixtures are perfectly suitable for all general-purpose applications found throughout the home, office, and warehouse. With a contemporary outlook, these fixtures are very convenient and easy to use and install. Having a durable polycarbonate lens, they will not yellow or change color. These low profile fixtures are designed for suspended chain mount and virtually eliminate maintenance as there are no costly bulbs to change. Perfect for task lighting, workshops, retail stores, closets and more, they are available in 4' length and come with a power cord, all mounting accessories and an on/off pull chain.



- Available 4 ft sizes •
- Operating temperature -4-113°F (-20-45°C) •
- 5-year warranty
- Greater than 50,000 hour L70 lifetime

Low profile design •



#### LED Flush Mount


Our LED Flush Mount fixtures are designed to replace outdated fluorescent and incandescent flush mount fixtures with bright, even light. Our traditional design and energy efficient technologies make this fixture an ideal choice for residential, commercial and hospitality applications.

12 5/8"

- Available in 10", 11" and 13" sizes
- Standard dimming
- Operating temperature -4-113°F (-20-45°C) Greater than 50,000 hour L70 lifetime •
- Low profile design
- 5-year limited warranty



18 = 18 W



**13** = 13"

#### I FD Round Mini Panel

ASD LED round mini panels are a great choice for indoor lighting in residential and commercial environments. Our dimmable round panels have low energy consumption, long life and a low profile design. These ETL fixtures are Energy Star qualified and simple to install.

- Low energy consumption
- Finish: white
- Easy to install •
- Damp Location rated •
- Dimmable with triac controls •
- Surface mount
- 5-year limited warranty >54,000 Hrs




	lighting facts		Size	Model	Watts	CCT	Lm	Pcs in a case	Equivalency
			6	ASD-MNPR-5D630-W ASD-MNPR-5D640-W	6 6	3,000 4,000	424 424	60 60	35W Inc 35W Inc
$\bigcirc$	lighting facts ()		7" 7"	ASD-MNPR-7D1230-W ASD-MNPR-7D1240-W	12 12	3,000 4,000	889 889	40 40	100W Inc 100W Inc
	lighting facts	<u>1/2"</u>	9" 9"	ASD-MNPR-9D1830-W ASD-MNPR-9D1840-W	18 18	3,000 4,000	1,341 1,341	20 20	150W inc 150W inc

Family	Size	Dimmable	Watts	CCT	Finish
ASD-MNPR		D			
LED Mini Panel Round	<b>5</b> = 5"		<mark>6</mark> = 6 W	<b>30</b> = 3,000 K	W = White
	<b>7</b> = 7"		<b>12</b> = 12 W	<b>40</b> = 4,000 K	
	<mark>9</mark> = 9"		<b>18</b> = 18 W		

### LED Retrofit Kit

ASD LED dimmable Recessed Retrofit Kits are the perfect upgrade for your existing recessed light fixture. We have 4" and 5"/6" kits available. These downlight retrofits are UL listed, Energy Star rated and suitable for damp location applications. Available in 2700 K and 4000 K color temperatures, our LED Recessed Retrofit kits are the perfect energy saving fixture for residential and commercial applications.

- Consumes up to 80% less energy •
- Suitable for dry and damp locations •
- Beam angle: 110°
- 5-year limited warranty



Family	Modification	Dimmable	nable Size Wa		CCT
ASD-DL	1	D			
LED Downlight			<b>4</b> = 4"	<b>7.5</b> = 7.5 W	<b>27</b> = 2,700 K
			<mark>6</mark> = 6"	<b>11.5</b> = 11.5 W	<mark>40</mark> = 4,000 K
				<mark>18</mark> = 18 W	



#### LED A19 Bulbs

ASD LED-A19 light bulbs provide beautiful, comfortable, warm light for your home. ASD Light bulbs were created with the homeowner in mind to produce natural looking, even light. These economically priced non-dimming bulbs are provide many years of life; lowering power consumption while also decreasing your energy usage. These are perfect for table lamps, chandeliers, ceiling fans, and wall fixtures.

- Replaces up to a 60W incandescent bulb
- 2-year limited warranty

• 10,000 hour LED Lifetime



		Туре	Model	Base	Watts	ССТ	Lm	Pcs in a case	Equivalency
		A19 ASD-LE A19 ASD-LE	D-A19N26-5.5-30 D-A19N26-5.5-40 D-A19N26-9-30 D-A19N26-9-40	26 26 26 26	5.5 5.5 9 9	3,000 4,000 3,000 4,000	450 450 800 800	100 100 100 100	40W Inc 40W Inc 60W Inc 60W Inc
Family	Туре	Non-dimmable	Base	ò		Watt	S	I	ССТ
ASD-LED	A19	N	26						
					5	. <mark>5</mark> = 5.5 W;	9 = 9 W	<b>30</b> = 3,000	K; <mark>40</mark> = 4,000 K

#### LED-BR30 Dimmable Bulbs

ASD LED-BR30 Dimmable light bulbs produce better, brighter light than a traditional incandescent recessed light. Designed to enhance colors and produce a more natural feeling, these bulbs are your best value for the money. Our BR30 bulbs are designed for use in 6" recessed light cans and many years of life for a fraction of the cost of a traditional bulb.

- Replaces up to a 65W incandescent bulb
- 3-year limited warranty

• 25,000 hour LED Lifetime

		Туре	Model	Base	Watts	CCT	Lm	Pcs in a case	Equivalency
c United and the second s	is		D-LED-BR30D26-10-30 D-LED-BR30D26-10-40	26 26	10 10	3,000 4,000	650 650	36 36	65W Inc 65W Inc
Family	Туре	Non-dimmable	Base			Watts		l	CCT
ASD-LED	BR30	N	26			10			



ASD Lighting Corp.

120 Shawmut Rd, Canton, MA 02021

#### www.asd-lighting.com

Phone: 781-739-3977 • Fax: 339-502-8970

Orders@asd-lighting.com for orders and quotes

New Standard In Lighting

For orders, questions, or if you simply want to take us out for a beer, please call your local ASD representative:

## 2017/2