




**OUTDOOR**



**LED INDOOR LIGHTING**



# ASD Lighting Corp.

---

ASD Lighting Corp started in Eastern Europe in 1999. Since that time, ASD has grown to become one of the largest lighting manufacturers in Eastern Europe with thousands of SKU's.

ASD opened in the US market in 2014 in Canton, MA and is one of the fastest growing LED luminaire manufacturers in the country. We produce high quality LED fixtures at aggressive prices making us the best value for the money in the market.

We have a massive amount of in-stock inventory in our 100,000 sq ft. warehouse in Massachusetts eliminating any lead time.

We offer fast reliable shipping and will ship orders the same day whenever possible.

We are the "New Standard in Lighting". We develop reliable quality fixtures with new energy saving technologies at affordable pricing.

ASD Lighting is 100% committed to the satisfaction of our customers and never stop improving.



## Certification

---

Our products are designed and engineered in Europe.

Our product development laboratory and skilled technical staff allow us to completely control the manufacturing process to produce high-quality, reliable lighting fixtures.

Our fixtures are put through rigorous testing to receive UL, ETL and FCC certification as well as DLC and Energy Star ratings.





# LED Edge-Lit Flat Panel

ASD Edge-Lit Flat Panels are the best choice for all recessed, suspended and surface mounted applications. Our panels are cULus and DLC approved\*. Available in DLC Standard and DLC Premium, these contemporary panels are only 1/2" thick making them one of the slimmest panels on the market. Up to 20 dimmable panels can be linked to each master panel. Hanging sets, surface mount kits and sheetrock kit options are available for a variety of installation options.



- Available in 1x4, 2x2 and 2x4 sizes
- High Efficiency DLC Standard and DLC Premium
- Recessed, suspended and surface mounting options
- Standard 0-10 V dimming
- 5-year limited warranty
- Standard 81,000 hour L70 lifetime
- Premium 139,000 hour L70 lifetime


\*Please check with DLC to determine your local rebate incentives based on DLC fixture rating



Type	Model	Watts	CCT	Lm	Pcs in a case	DLC	Equivalency
------	-------	-------	-----	----	---------------	-----	-------------



### 85 lm/w

1x4	ASD-ELP14D4050	40	5,000	3,400	4	3.0	75W FL
2x2	ASD-ELP22D4050	40	5,000	3,813	4	3.0	75W FL



### 110 lm/w

1x4	ASD-ELP14D2735HE	27	3,500	3,054	4	4.2 Standard	65W FL
2x2	ASD-ELP22D2235HE	22	3,500	2,380	4	4.2 Standard	55W FL
2x2	ASD-ELP22D2250HE	22	5,000	2,477	4	4.2 Standard	55W FL
2x2	ASD-ELP22D2735HE	27	3,500	3,056	4	4.2 Standard	65W FL
2x2	ASD-ELP22D2750HE	27	5,000	3,166	4	4.2 Standard	65W FL
2x2	ASD-ELP22D2765HE	27	6,500	3,208	4	4.2 Standard	65W FL
2x2	ASD-ELP22N2740HE	27	4,000	3,131	2	NO	65W FL
2x4	ASD-ELP24D4035HE	40	3,500	4,372	2	4.2 Standard	98W FL



### 120 lm/w

1x4	ASD-ELP14D4040STD	40	4,000	4,433	4	4.2 Standard	120W FL
2x2	ASD-ELP22D2735STD	27	3,500	3,051	4	4.2 Standard	65W FL
2x2	ASD-ELP22D2740STD	27	4,000	3,296	4	4.2 Standard	65W FL
2x2	ASD-ELP22D2750STD	27	5,000	3,189	4	4.2 Standard	65W FL
2x2	ASD-ELP22D3640	36	4,000	4,350	2	4.2 Standard	110W FL
2x4	ASD-ELP24D4035STD	40	3,500	4,571	2	4.2 Standard	96W FL
2x4	ASD-ELP24D4040STD	40	4,000	4,974	2	4.2 Standard	96W FL
2x4	ASD-ELP24D4050STD	40	5,000	5,156	2	4.2 Standard	96W FL

### 130 lm/w

2x2	ASD-ELP22D2740PRM	27	4,000	3,520	4	4.2 Premium	75W FL
-----	-------------------	----	-------	-------	---	-------------	--------

### 140 lm/w

2x4	ASD-ELP24D4040PRM	40	4,000	5,787	2	4.2 Premium	160W FL
-----	-------------------	----	-------	-------	---	-------------	---------

Family	Size	Dimmable	Watts	CCT	Series
ASD-ELP		D			
Edge-Lit Panel	14 = type 1x4		22 = 22 W	35 = 3,500 K	HE
	22 = type 2x2		27 = 27 W	40 = 4,000 K	STD
	24 = type 2x4		36 = 36 W	50 = 5,000 K	PRM
			40 = 40 W	65 = 6,500 K	
			60 = 60 W		

# LED Direct-Lit Panel



ASD Direct-Lit Panels are a great economical choice for an easy direct replacement for recessed panel lighting. They are sold in pairs and are cULus listed and DLC approved\*. Once installed, these panels have the look of a standard fluorescent fixture with a prismatic lens, but are only 1" thick. Our panels are reasonably priced, maintenance free and can significantly reduce your energy bills. Up to 20 dimmable panels can be linked to each master panel.



- Available in 2x2 and 2x4 sizes
- Standard 0-10 V dimming
- Greater than 100,000 hour L70 lifetime
- Recessed mounting
- 5-year limited warranty

\*Please check with DLC to determine your local rebate incentives based on DLC fixture rating

Type	Model	Watts	CCT	Lm	Pcs in a case	DLC	Equivalency
<b>90 lm/w</b>							
2x2	ASD-DLP22D4040	40	4,000	3,761	2	3.0	80W FL
2x2	ASD-DLP22D4050	40	5,000	3,707	2	3.0	80W FL
2x4	ASD-DLP24D6040	60	4,000	5,310	2	3.0	120W FL
2x4	ASD-DLP24D6050	60	5,000	5,492	2	3.0	120W FL
<b>110 lm/w</b>							
2x2	ASD-DLP22D2735HE	27	3,500	3,240	2	4.2 Standard	65W FL
2x2	ASD-DLP22D2740HE	27	4,000	3,385	2	4.2 Standard	65W FL
2x2	ASD-DLP22D2750HE	27	5,000	3,420	2	4.2 Standard	65W FL
2x4	ASD-DLP24D4035HE	40	3,500	4,240	2	4.2 Standard	98W FL
2x4	ASD-DLP24D4040HE	40	4,000	4,320	2	4.2 Standard	98W FL




Family	Size	Dimmable	Watts	CCT	Series
ASD-DLP		D			HE
Direct-Lit Panel	22 = type 2x2 24 = type 2x4		22 = 22 W 27 = 27 W 40 = 40 W 60 = 60 W	35 = 3,500 K 40 = 4,000 K 50 = 5,000 K	

# LED Driver with a Mounting Box

Engineered for a long life of high performance, our drivers are a vital component to our panels. ASD drivers come with a quick disconnect plug (85 and 110lm/w models) and all have 0-10v dimming. This product comes with a 5-year warranty.



Model	Power	Input Voltage	Output Voltage	Max Current	Product Code	Pcs in one carton
ASD-BLP22D	22 W	100-277 V	30-42 V	500 mA	027.0104	4
ASD-BLP27D	27 W	100-277 V	30-42 V	700 mA	027.0103	4
ASD-BLP40D	40 W	100-277 V	30-42 V	1,050 mA	027.0101	4
ASD-BLP60D	60 W	100-277 V	30-42 V	1,500 mA	027.0102	4



Family	Dimmable	Watts
ASD-BLP	D	
Driver for LED Panel		22 = 22 W; 27 = 27 W; 40 = 40 W; 60 = 60 W

# Accessories for LED Edge-Lit Flat Panels

## FRAME FOR SURFACE MOUNTING


only for LED Edge-Lit Flat Panels

LED panels are easily mounted on horizontal or sloped surfaces with our surface mount frame.

Model	Dimensions	Pcs in a case
ASD-FELP14	48" x 12" x 2.4"	9
ASD-FELP22	24" x 24" x 2.4"	9
ASD-FELP24	48" x 24" x 2.4"	9



Family	Size
<b>ASD-FELP</b>	
Frame for Edge-Lit Panel	14 = type 1x4 22 = type 2x2 24 = type 2x4






## FRAME FOR RECESSED SHEETROCK MOUNT

for LED Edge-Lit and Direct-Lit Panels

Allows for flush mounting into a sheetrock ceiling.

Model	Dimensions	Pcs in a case
ASD-FDW-ELP14	47 1/2" x 11 3/8" x 1"	20
ASD-FDW-ELP22	25 1/4" x 25 1/4" x 1"	20
ASD-FDW-ELP24	49 1/4" x 25 1/4" x 1"	20

Family	Size
<b>ASD-FDW-ELP</b>	
Frame for Dry Wall	14 = type 1x4 22 = type 2x2 24 = type 2x4




## HANGING SET


only for 2x2 and 1x4 LED Edge-Lit Flat Panels

This kit contains four suspension wires, anchors and screws. You will be able to adjust the length of the suspension wires to your desired fixture height allowing you to hang from flat or sloped ceilings.

Model	Dimensions (L)	Pcs in a case
ASD-CHS4	4"	50
ASD-CHS6	6"	50



Family	Dimensions
<b>ASD-CHS</b>	
Ceiling Hanging set	4 = 4" 6 = 6"



# LED SMD Floodlight

The ASD DLC 3.0 approved and UL listed LED SMD Floodlights are the best choice for all floodlight applications. Brightly illuminate walkways, parking areas, building entrances and more. Durable high quality and performance in an affordable price range.

- Resistant to high and low temperatures
- Operating temperature -40-122°F (-40-50°C)
- Suitable for wet locations, degree of protection
- High performance Advanced SMD technology
- 5-year limited warranty - >50,000 Hrs
- Low energy consumption



\*Please check with DLC to determine your local rebate incentives based on DLC fixture rating


					Model	Watts	CCT	Lm	Pcs in a case	DLC	Equivalency
					ASD-SFL2040	20	4,000	1,560	4	3.0	70W MH
					ASD-SFL2050	20	5,000	1,615	4	3.0	70W MH
					ASD-SFL3040	30	4,000	2,365	4	3.0	100W MH
					ASD-SFL3050	30	5,000	2,441	4	3.0	100W MH
					ASD-SFL5040	50	4,000	3,880	4	3.0	180W MH
					ASD-SFL5050	50	5,000	4,123	4	3.0	180W MH
					ASD-SFL7540	75	4,000	6,084	4	3.0	270W MH
					ASD-SFL7550	75	5,000	6,420	4	3.0	270W MH
					ASD-SFL10040	100	4,000	7,783	4	3.0	350W MH
					ASD-SFL10050	100	5,000	8,304	4	3.0	350W MH
					ASD-SFL15040	150	4,000	11,343	4	3.0	540W MH
					ASD-SFL15050	150	5,000	11,927	4	3.0	540W MH

Family	Watts	CCT
ASD-SFL		
LED SMD Floodlight	20 = 20 W; 30 = 30 W 50 = 50 W; 75 = 75 W 100 = 100 W; 150 = 150 W	50 = 5,000 K

## POLE MOUNTING BRACKET

Our Pole mount bracket allows you to easily attach our LED SMD Floodlights to our adapter bracket for pole mount applications.



Model	Dimensions	Pcs in a case
ASD-PMB-FL	7.9"x3.2"x3.5"	20

# LED SMD Compact Floodlight with knuckle



Our UL and DLC 4.2 Compact Flat floodlights measure around 1 inch thick making it one of the thinnest, yet durable floodlights on the market today. Using LED SMD advanced technology, our floods will outperform most others with ease. These are perfect for commercial and residential applications and easy to install with the adjustable knuckle mount. They are a top choice for illuminating driveways, parking lots, buildings, entryways and signs.

- Resistant to high and low temperatures; operating temperature -4-104°F (-40-40°C)
- Suitable for wet locations IP 65
- High performance Advanced SMD technology
- 5-year limited warranty - >36,000 Hrs
- Low energy consumption



\*Please check with DLC to determine your local rebate incentives based on DLC fixture rating

Model	Watts	CCT	Lm	DLC	Equivalency
ASD-CSFL-A1050	10	5,000	1,029	4.2	35W MH
ASD-CSFL-A2050	20	5,000	1,865	4.2	75W MH
ASD-CSFL-A3050	30	5,000	2,877	4.2	100W MH
ASD-CSFL-A5050	50	5,000	4,872	4.2	180W MH

Family	Watts	CCT
ASD-CSFL		
LED SMD COMPACT Floodlight	10 = 10 W; 20 = 20 W 30 = 30 W; 50 = 50 W	50 = 5,000 K

# LED SMD Bullet Floodlight with knuckle



ASD LED SMD Bullet Flood lights uses the latest in solid state lighting technology for high efficiency, long life and low maintenance. This fixture is perfect for facade, landscape and sign lighting applications. Sealed to keep out dirt, bugs and moisture, the Bullet Floods are constructed with a precision die-cast aluminum housing and tempered, shatter-resistant glass for a sleek appearance and maximum durability.

- Resistant to high and low temperatures; operating temperature -40-104°F (-40-40°C)
- Suitable for wet locations IP 65
- ½" NPS threaded locking swivel arm
- 5-year limited warranty - >54,000 Hrs



Model	Watts	CCT	Lm	Pcs in a case	DLC	Equivalency
ASD-BFL-A15N50	15	5,000	1,701	12	4.2 Standard	70W MH
ASD-BFL-A28N50	28	5,000	2,990	8	4.2 Standard	150W MH

Family	Knuckle	Watts	Non-dimmable	CCT
ASD-BFL	A	15 = 15 W; 28 = 28 W	N	50 = 5,000 K
LED Bullet Floodlight	with knuckle			

## LED SMD Wallpack

ASD LED Wall Packs feature leading-edge optics that increase light output and reduce shadows to create safe, brightly-lit outdoor environments in parking garages, entrances, schools, hospitals, hotels, public areas and outdoor walkways. There is an optional Glare Shield available for dark sky compliance. The shield will help to minimize blue light emissions and light the area that needs it.

- Operating temperature -40-104°F (-40-40°C)
- Standard 0-10V dimming (80W model only)
- Suitable for wet locations – IP 65
- Durable borosilicate prismatic glass lens
- Greater than 54,000 hour LED lifetime
- 5-year warranty
- Low energy consumption




Model	Watts	CCT	Lm	Pcs in a case	DLC	Equivalency
ASD-WLP01-50N50	50	5,000	5,969	1	4.2 Standard	175W MH
ASD-WLP01-80D50	80	5,000	9,953	1	4.2 Standard	2*150W MH

Family	Modification	Watts	Dimmable	CCT
ASD-WLP LED Wallpack	01	50 = 50 W; 80 = 80 W	N = Non-dimmable D = Dimmable	50 = 5,000 K

### GLARE SHIELD AVAILABLE (OPTIONAL)

Optional shield will help to minimize blue light emissions and light the area that needs it.



Model	Dimensions	Pcs in a case
ASD-SWLP01-50/80	12 13/16"x9 1/2"x10 1/8"	8

## LED COB Cutoff Wallpack

Our slim LED wallpacks are designed to replace up to a 400w metal halide producing an abundance of light with a fraction of the power. These durable low profile fixtures are great in a downlight or uplight application and are easily installable. Reduce shadows to create safe, brightly lit exterior environments for commercial buildings, schools, hospitals, hotels and more.

- Resistant to high and low temperatures; operating temperature -40-104°F (-40-40°C)
- Suitable for wet locations, degree of protection IP 65
- 5-year limited warranty
- Low energy consumption
- Greater than 36,000 hour LED lifetime



Model	Watts	CCT	Lm	Pcs in a case	DLC	Equivalency
ASD-WLP02-30N50	30	5,000	2,716	8	4.2 Standard	100W MH
ASD-WLP02-50N50	50	5,000	4,542	8	4.2 Standard	150W MH

Model	Watts	CCT	Lm	Pcs in a case	DLC	Equivalency
ASD-WLP02-75N50	75	5,000	7,044	4	4.2 Standard	250W MH
ASD-WLP02-100N50	100	5,000	10,277	4	4.2 Standard	2*150W MH

Family	Modification	Watts	Non-dimmable	CCT
ASD-WLP LED Wallpack	02	30 = 30 W; 50 = 50 W 75 = 75 W; 100 = 100 W	N	50 = 5,000 K

# LED SMD Adjustable Cutoff Wallpack



Our LED SMD adjustable wall packs feature a hinged bracket to allow for simple beam angle adjustment. They are designed to replace up to a 400w metal halide producing an abundance of light with a fraction of the power. These low profile durable fixtures are great for a downlight or uplight and are easily installable. This is an ideal commercial outdoor fixture for buildings, parking garages, schools, and warehouses, is suitable for wet locations and harsh environments.



- Fixture head pivots fully up to 90°
- Suitable for wet locations, degree of protection IP 65
- Operating temperature -40-104°F (-40-40°C)
- Standard 0-10V dimming (80W and 120W models only)
- 5-year limited warranty
- Greater than 54,000 hour LED lifetime

Model	Watts	CCT	Lm	Pcs in a case	DLC	Equivalency
ASD-WLP02A-12N50B	12	5,000	1,321	12	4.2 Standard	70W MH
ASD-WLP02A-30N50B	30	5,000	3,298	4	4.2 Standard	150W MH
ASD-WLP02A-50N50B	50	5,000	5,287	4	4.2 Standard	175W MH
ASD-WLP02A-80D50B	80	5,000	9,241	2	4.2 Standard	2*150W MH
ASD-WLP02A-120D50B	120	5,000	14,227	2	4.2 Standard	400W MH

Family	Modification	Watts	Dimmable	CCT
ASD-WLP	02A	12 = 12 W; 30 = 30 W; 50 = 50 W 80 = 80 W; 120 = 120 W	N N = Non-dimmable D = Dimmable	50 = 5,000 K

# LED SMD Full Cutoff Wallpack

ASD Full Cutoff Wallpacks offer controlled light output for general-purpose area and security lighting and are Dark-sky compliant. They are made with a die-cast aluminum housing and dark bronze finish. Our Full Cutoff LED wall pack is a perfect replacement for traditional outdoor wall packs.



- Fixture is full cutoff version (no uplight)
- Impact-resistant polycarbonate optical lens
- Operating temperature -40-104°F (-40-40°C)
- Standard 0-10V dimming (80W model only)
- Suitable for wet locations, degree of protection IP 65
- 5-year limited warranty
- Greater than 54,000 hour LED lifetime

Model	Watts	CCT	Lm	Pcs in a case	DLC	Equivalency
ASD-WLP03-50N50	50	5,000	5,798	1	4.2 Standard	175W MH
ASD-WLP03-80D50	80	5,000	9,128	1	4.2 Standard	2*150W MH


Family	Modification	Watts	Dimmable	CCT
ASD-WLP	03	50 = 50 W; 80 = 80 W	N = Non-dimmable D = Dimmable	50 = 5,000 K

# LED Security Wallpack

ASD LED SMD Security Wallpacks with integrated dusk to dawn photocell sensor provide optimal illumination for commercial and industrial environments. This fixture is ideal for outdoor applications such as doorways, loading areas, walkways, post mounted applications and more.



- Tough polycarbonate lens for increased vandal resistance
- Advanced LED SMD technology
- Built in photocell for dusk to dawn timing
- Operating temperature -40-104°F (-40-40°C)
- Suitable for wet locations – IP 65
- 5-year limited warranty
- Greater than 54,000 hour LED lifetime



Model	Watts	CCT	Lm	Pcs in a case	DLC	Equivalency
ASD-WLP04-20N50-PC	20	5,000	2,160	6	4.2 Standard	80W MH


Family	Modification	Watts	Dimmable	CCT	Photocell
ASD-WLP	04	20 = 20 W	Non-dimmable	50 = 5,000 K	PC

# LED Area and Roadway Lighting

ASD LED Area and Roadway Lighting with dusk to dawn photocell offers security and safety and can be mounted to buildings or posts to fully illuminate areas such as doorways, garages, sheds, barns, driveways and more.



- Twist-lock photocell included
- Mounts directly or with mounting arm (included)
- Durable Die-Cast Aluminum Housing
- Suitable for wet locations – IP 65
- Operating temperature -40-104°F (-40-40°C)
- 5-year limited warranty
- Greater than 54,000 hour LED lifetime



Model	Watts	CCT	Lm	Pcs in a case	DLC	Equivalency
ASD-ARL-50N50-PC	50	5,000	5,326	1	4.2 Standard	175W MH


Family	Watts	Dimmable	CCT	Photocell
ASD-ARL	50 = 50 W	Non-dimmable	50 = 5,000 K	PC

LED Area and Roadway light

# LED SMD Canopy

ASD LED Canopy Lights are wet location rated and designed to withstand the elements while producing a substantial amount of light. This is an ideal replacement for an old, energy wasting halogen. Our Canopy is equipped with Advanced SMD technology for superior light output. There are no costly bulbs to change, virtually eliminating maintenance for years to come.

- Available in 30W, 50W and 75W
- High efficiency – 105 lm/w
- Greater than 36,000 hour LED lifetime
- 5-year limited warranty
- Resistant to high and low temperatures
- Operating temperature -40-104°F (-40-40°C)
- Black or white finish




Model	Watts	CCT	Lm	Pcs in a case	DLC	Equivalency
ASD-CAN01-30N50	30	5,000	3,178	8	4.2 Standard	150W MH
ASD-CAN01-30N50-W	30	5,000	3,178	8	4.2 Standard	150W MH
ASD-CAN01-50N50	50	5,000	5,695	8	4.2 Standard	175W MH
ASD-CAN01-50N50-W	50	5,000	5,695	8	4.2 Standard	175W MH
ASD-CAN01-75N50	75	5,000	8,406	8	4.2 Standard	2*150W MH
ASD-CAN01-75N50-W	75	5,000	8,406	8	4.2 Standard	2*150W MH

Family	Modification	Watts	Non-dimmable	CCT	Finish
ASD-CAN	01		N		
LED Canopy		30 = 30 W; 50 = 50 W 75 = 75 W		50 = 5,000 K	Black; W = White

# LED SMD UFO HIGH BAY - WET LOCATION

Our New UFO style round high bay is the latest in LED technology. Smaller, more efficient, and longer lasting, our new IP65 – WET location rated LED UFO high bay fixture is at 130lm/w achieving desired light levels while using less power per fixture than most other LED High bay fixtures. Light can be dimmed to ideal brightness levels to save energy and achieve the exact light level needed for your application.

- Available in 100W, 150W and 200W
- High efficiency – 130 lm/w and up
- Greater than 54,000 hour L70 lifetime
- 5-year limited warranty
- Resistant to high and low temperatures; operating temperature -20-113°F (-30-45°C)



Model	Watts	CCT	Lm	Pcs in a case	DLC	Equivalency
ASD-UHB1-100D50PRM	100	5,000	13,519	1	4.2 Premium	400W MH
ASD-UHB1-150D50PRM	150	5,000	20,401	1	4.2 Premium	2*250W MH
ASD-UHB1-200D50PRM	200	5,000	26,895	1	4.2 Premium	600W MH

Family	Modification	Watts	Dimmable	CCT	Series
ASD-UHB	1		D		PRM
LED UFO High Bay		100 = 100 W; 150 = 150 W 200 = 200 W		50 = 5,000 K	Premium


# LED SMD UFO HIGH BAY with J-Box

Our LED SMD cutting edge UFO High Bay is smaller, long lasting and extremely efficient. Less than 13 inches in diameter, this compact fixture really delivers high performance without sacrificing quality. The UHB5 series delivers efficient, uniform, high lumen output for high bay and low bay applications in industrial, commercial and retail environments. Included is an optional 3 in 1 dimming function (0-10vdc, PWM signal or resistance) to dim to desired light levels. Our innovative design with steel junction box on top of the fixture has two 1/2" knockouts and two 3/4" knockouts and makes installation fast and simple with hook and pendant mount options.



- Available in 100W, 150W and 200W
- Greater than 54,000 hour L70 lifetime
- High efficiency - 130 lm/W and up
- 5-year limited warranty
- 100-277V and 480V options
- Operating temperature -20-113°F (-30-45°C)

Model	Watts	CCT	Lm	Pcs in a case	DLC	Equivalency
ASD-UHB5-100D50PRM	100	5,000	13,460	1	4.2 Premium	400W MH
ASD-UHB5-150D50PRM	150	5,000	19,902	1	4.2 Premium	2*250W MH
ASD-UHB5-200D50PRM	200	5,000	26,499	1	4.2 Premium	600W MH
ASD-UHB5HV-200D50PRM	200	5,000	28,134	1	4.2 Premium	600W MH



Family	Modification	Watts	Dimmable	CCT	Series
ASD-UHB			D		PRM
LED UFO High Bay	5 5HV = High Voltage	100 = 100 W; 150 = 150 W 200 = 200 W		50 = 5,000 K	Premium

## Accessories for UFO High Bay and UFO High Bay with j-box

UFO High Bay optional accessories are available to customize the fixture to your needs. These options include an inline wire connector for power cable, a polycarbonate diffuser and a polycarbonate bottom conical lens or aluminum diffuser.

Image	Model	Materials	Pcs in a case
<div style="display: flex; justify-content: space-around;"> <div style="text-align: center;"> <p>Female</p> </div> <div style="text-align: center;"> <p>Male</p> </div> </div>	LLT-M19CS03	Aluminum	1000
<div style="display: flex; justify-content: space-around;"> <div style="text-align: center;"> <p>ASD-DUHB-16-90PC</p> </div> <div style="text-align: center;"> <p>ASD-DUHB-19-90PC</p> </div> </div>	ASD-DUHB-16-90PC ASD-DUHB-19-90PC	Polycarbonate Polycarbonate	10 10
<div style="display: flex; justify-content: space-around;"> <div style="text-align: center;"> <p>ASD-BLUHB-16PC</p> </div> <div style="text-align: center;"> <p>ASD-BLUHB-19PC</p> </div> </div>	ASD-BLUHB-16PC ASD-BLUHB-19PC	Polycarbonate Polycarbonate	10 10
<div style="display: flex; justify-content: space-around;"> <div style="text-align: center;"> <p>ASD-DUHB-16-90AL</p> </div> <div style="text-align: center;"> <p>ASD-DUHB-21-90AL</p> </div> </div>	ASD-DUHB-16-90AL ASD-DUHB-21-120ALG	Aluminum Aluminum	20 10

# Round High Bay

The ASD Series LED Round High Bay provides high performance at very affordable pricing eliminating the need for outdated, energy wasting high bay luminaires. Perfect for gymnasiums, warehouses, industrial facilities and other commercial high bay applications, our unique lightweight aluminum alloy design with loop heat pipe allows for excellent heat dissipation. The luminaire is made with a dimmable driver for excellent stability, high performance and long life.



- Available in 100W, 150W and 200W
- High efficiency - 120 lm/w
- Greater than 68,000 hour L70 lifetime
- 5-year limited warranty
- Resistant to high and low temperatures; operating temperature -4-131°F (-20-55°C)

Image	UL LISTED DLC FC	Dimensions	Model	Watts	CCT	Lm	Pcs in a case	DLC	Equivalency
	UL LISTED DLC FC	10 3/4" x 8 1/4" x 9 1/4"	ASD-LRHB1-100D35HE	100	3,500	11,603	4	4.2 Standard	250W MH
		ASD-LRHB1-100D50HE	100	5,000	11,940	4	4.2 Standard	250W MH	
	UL LISTED DLC FC	10 3/4" x 9 1/4" x 9 1/4"	ASD-LRHB1-150D35HE	150	3,500	17,729	4	4.2 Standard	1*400W MH
		ASD-LRHB1-150D50HE	150	5,000	18,258	4	4.2 Standard	1*400W MH	
	UL LISTED DLC FC	10 3/4" x 10 1/2" x 9 5/16"	ASD-LRHB1-200D50HE	200	5,000	24,756	2	4.2 Standard	2 * 250W MH

Family	Modification	Watts	Dimmable	CCT	Series
ASD-LRHB	1	100 = 100 W; 150 = 150 W 200 = 200 W	D	35 = 3,500 K 50 = 5,000 K	HE
LED Round High Bay					

# Accessories for Round High Bay

Round High Bay optional accessories are available to customize the fixture to your needs. These options include a polycarbonate diffuser and a polycarbonate bottom conical lens or aluminum diffuser.

Image	Model	Materials	Pcs in a case
 16 3/4" x 9 1/16"	ASD-DRHB-16AL	Aluminum	10
 16 1/8" x 10 1/2"	ASD-DRHB-16PC	Polycarbonate	10
 18 3/8" x 12"	ASD-DRHB-19PC	Polycarbonate	10
 16" x 1 1/4"	ASD-BLRHB-16PC	Polycarbonate	10
 18 3/4" x 1 5/8"	ASD-BLRHB-19PC	Polycarbonate	10

# Linear High Bay

ASD Linear High bays are the perfect replacement for T5/T8 /T12 florescent and are capable of replacing up to 500w MH with only 180w. Our LED High-Bay fixtures are maintenance free and meet the harsh performance requirements of commercial and industrial environments with high quality, high efficiency and high lumen output to save you money. They are UL, DLC and motion sensor and DALI LED compatible.









- Up to 24,000 Lumens
- High efficiency - 130 lm/w
- Resistant to high and low temperatures; operating temperature -4-131°F (-20-55°C)
- Standard 0-10 V dimming
- 5-year limited warranty
- Greater than 139,000 hour L70 lifetime

Type	Model	Watts	CCT	Lm	Pcs in a case	DLC	Equivalency
4 ft	ASD-WHB-4D9040HE	90	4,000	12,256	1	4.2 Standard	4*T8 32W FL; 250W MH
	ASD-WHB-4D9050HE	90	5,000	12,527	1	4.2 Standard	4*T8 32W FL; 250W MH
4 ft	ASD-WHB-4D14040HE	140	4,000	18,798	1	4.2 Standard	1*400W MH
	ASD-WHB-4D14050HE	140	5,000	18,944	1	4.2 Standard	1*400W MH
4 ft	ASD-WHB-4D18040HE	180	4,000	24,118	1	4.2 Standard	2* 250W MH
	ASD-WHB-4D18050HE	180	5,000	24,587	1	4.2 Standard	2* 250W MH

Family	Size	Dimmable	Watts	CCT	Series
ASD-WHB	4 = 4 ft	D	90 = 90 W; 140 = 140 W 180 = 180 W	40 = 4,000 K 50 = 5,000 K	HE

# Accessories for Linear High Bay

ASD Lighting offers optional accessories for our warehouse high bay fixtures making them suitable for most applications. These accessories include a lens consisting of a PS prismatic cover and an iron frame, and a wire guard made of steel wire with metal clips for attachment.

	Model	Pcs in a case
 <p>Lens for WHB4D90</p> <p>48 1/4"</p> <p>11 5/8"</p> <p>13/16"</p>	ASD-LWHB90	10
 <p>Lens for WHB4D140</p> <p>48 1/4"</p> <p>15 1/4"</p> <p>13/16"</p>	ASD-LWHB140	10
 <p>Lens for WHB4D180</p> <p>48 1/4"</p> <p>19 1/2"</p> <p>13/16"</p>	ASD-LWHB180	10
 <p>Wire Guard for WHB4D90</p> <p>48 1/4"</p> <p>11 3/8"</p> <p>1"</p>	ASD-GWHB90	10
 <p>Wire Guard for WHB4D140</p> <p>48 1/4"</p> <p>14 15/16"</p> <p>1"</p>	ASD-GWHB140	10
 <p>Wire Guard for WHB4D180</p> <p>48 1/4"</p> <p>19 1/4"</p> <p>1"</p>	ASD-GWHB180	10
 <p>Bracket for Pendant stem mounting WHB</p> <p>4 1/2"</p> <p>2 9/16"</p> 	ASD-TMB-WHB	20


# LED Vaporproof Fixture

ASD Vapor Proof fixtures are the logical choice for harsh applications such as car washes, garages, stairwells, commercial kitchens, walk-in coolers, etc. These are IP66 rated making them dustproof and ideal for wet locations. Our Vapor proof fixtures are made from a polycarbonate housing and never lose their luster.




- Available in 4ft size
- Resistant to high and low temperatures; operating temperature -4-104°F (-20-40°C)
- High efficiency - 110 lm/w
- Suitable for wet locations - IP66 rated
- 5-year limited warranty
- Greater than 83,000 hour L70 lifetime

## Opaque Lens



Type	Model	Watts	CCT	Lm	Pcs in a case	DLC	Equivalency
4 ft	ASD-LVP-4N3135MHE	31	3,500	3,663	9	4.2 Standard	76W FL
4 ft	ASD-LVP-4N3140MHE	31	4,000	3,678	9	4.2 Standard	76W FL
4 ft	ASD-LVP-4N3150MHE	31	5,000	3,798	9	4.2 Standard	76W FL

## Clear Lens



4 ft	ASD-LVP-4N3140CHE	31	4,000	3,569	9	4.2 Standard	76W FL
4 ft	ASD-LVP-4N3150CHE	31	5,000	3,642	9	4.2 Standard	76W FL


Family	Size	Non-dimmable	Watts	CCT	Lens	Series
ASD-LVP	4	N				HE
LED VaporProof	4 = 4 ft		31 = 31 W	35 = 3,500 K 40 = 4,000 K 50 = 5,000 K	M = Opaque Lens C = Clear Lens	

# Seamless LED Vaporproof Fixture


Our cutting edge Seamless Vapors are a contemporary version of the typical vapor proof fixture. This sleek new seamless design has a one piece body eliminating the need for clips. It has 4 gasketed screws and a gasketed end cap on both sides for easy connection. The body is polycarbonate, not plastic making this extremely durable and able to withstand water, dust, chemicals and maintain its color and luster. We have 110lm/w Standard non-dimmable and a new 125lm/w Premium 0-10v dimmable.



- Available in 4 ft and 8 ft sizes
- Resistant to high and low temperatures; operating temperature -4-104°F (-20-40°C)
- Suitable for wet locations - IP66 rated
- Vandal Proof
- 110 lm/W Standard and 125 lm/W Premium
- 5-year limited warranty, greater than 139,000 hour L70 lifetime



Type	Model	Watts	CCT	Lm	Pcs in a case	DLC	Equivalency
4 ft	ASD-LVP2SM-4N3135HE	31	3,500	3,425	9	4.2 Standard	76W FL
4 ft	ASD-LVP2SM-4N3140HE	31	4,000	3,450	9	4.2 Standard	76W FL
4 ft	ASD-LVP2SM-4N3150HE	31	5,000	3,505	9	4.2 Standard	76W FL
4 ft	ASD-LVP2SM-4D3140PRM	31	4,000	3,861	9	4.2 Premium	90W FL
4 ft	ASD-LVP2SM-4D3150PRM	31	5,000	3,860	9	4.2 Premium	90W FL



8 ft	ASD-LVP2SM-8N6035HE	60	3,500	6,904	4	4.2 Standard	148W FL
8 ft	ASD-LVP2SM-8N6040HE	60	4,000	6,960	4	4.2 Standard	148W FL
8 ft	ASD-LVP2SM-8N6050HE	60	5,000	7,020	4	4.2 Standard	148W FL
8 ft	ASD-LVP2SM-8D6040PRM	60	4,000	7,721	4	4.2 Premium	175W FL
8 ft	ASD-LVP2SM-8D6050PRM	60	5,000	7,721	4	4.2 Premium	175W FL

Family	Modification	Type	Lens	Size	Dimmable	Watts	CCT	Series
ASD-LVP	2	S						
LED VaporProof		Seamless	M = Translucent white Lens	4 = 4 ft 8 = 8 ft	N = Non-dimmable D = Dimmable	31 = 31 W 60 = 60 W	35 = 3,500 K 40 = 4,000 K 50 = 5,000 K	HE PRM

# LED Striplight Fixture

Our High performance, 0-10v dimmable one lamp and two lamp fixtures have the standard look of a strip light but with a contemporary flair. These low profile fixtures are able to be linked together for a seamless look with our included quick-connect to reduce installation time significantly. ASD LED Striplights have a strong polycarbonate lens, are maintenance free and will significantly reduce energy consumption.

- Available in 2 ft and 4 ft lengths
- Operating temperature -4-113°F (-20-45°C)
- Low profile design
- 5-year warranty
- Greater than 100,000 hour L70 lifetime



Type	Model	Watts	CCT	Lm	Pcs in a case	DLC	Equivalency
2 ft	ASD-LSF-2D1040	10	4,000	1,100	6	4.2 Standard	34W FL
2 ft	ASD-LSF-2D2040	20	4,000	2,200	6	4.2 Standard	51W FL
4 ft	ASD-LSF-4D4040	40	4,000	4,400	6	4.2 Standard	96W FL

Family	Size	Dimmable	Watts	CCT
ASD-LSF		D		
LED Striplight fixture	2 = 2 ft; 4 = 4 ft		10 = 10 W; 20 = 20 W; 40 = 40 W	40 = 4,000 K

# LED Striplight Fixture Premium Series

ASD LED Strip lights are the perfect replacement for a fluorescent fixture. These fixtures are pendant or surface mounted and practically eliminate maintenance, as there are no costly bulbs to change. Perfect for task lighting, workshops, retail stores, coves, storage, display cases and more, they are available in 4' lengths and are able to quickly and easily be linked together for a seamless look.

- Available in 4 ft length
- Multiple fixtures may be linked together
- Fixture may be pendant, or surface mounted
- 5-year warranty
- Greater than 54,000 hour L70 lifetime



Type	Model	Watts	CCT	Lm	Pcs in a case	DLC	Equivalency
4 ft	ASD-LSF2-4D2440PRM	24	4,000	3,152	4	4.2 Premium	80W FL
4 ft	ASD-LSF2-4D4040PRM	40	4,000	5,205	4	4.2 Premium	150W FL

Family	Modification	Size	Dimmable	Watts	CCT	Series
ASD-LSF	2		D			PRM
LED Striplight fixture		4 = 4 ft		24 = 24 W; 40 = 40 W	40 = 4,000 K	Premium

# LED Shoplight Fixture

ASD LED Shoplight Fixtures are perfectly suitable for all general-purpose applications found throughout the home, office, and warehouse. With a contemporary outlook, these fixtures are very convenient and easy to use and install. Having a durable polycarbonate lens, they will not yellow or change color. These low profile fixtures are designed for suspended chain mount and virtually eliminate maintenance as there are no costly bulbs to change. Perfect for task lighting, workshops, retail stores, closets and more, they are available in 4' length and come with a power cord, all mounting accessories and an on/off pull chain.



- Available 4 ft sizes
- Operating temperature -4-113°F (-20-45°C)
- Low profile design
- 5-year warranty
- Greater than 50,000 hour L70 lifetime

Type	Model	Watts	CCT	Lm	Pcs in a case	ES	Equivalency
4 ft	ASD-LSH-4N4840	48	4,000	4,000	4	Energy Star listed	96 FL

Family	Size	Non-dimmable	Watts	CCT
ASD-LSH	4 = 4 ft	N	48 = 48 W	40 = 4,000 K
LED Shoplight fixture				

# LED Flush Mount

Our LED Flush Mount fixtures are designed to replace outdated fluorescent and incandescent flush mount fixtures with bright, even light. Our traditional design and energy efficient technologies make this fixture an ideal choice for residential, commercial and hospitality applications.

- Available in 10", 11" and 13" sizes
- Standard dimming
- Operating temperature -4-113°F (-20-45°C)
- Low profile design
- 5-year limited warranty
- Greater than 50,000 hour L70 lifetime



Type	Model	Watts	CCT	Lm	Pcs in a case	ES	Equivalency
10"	ASD-LFM-10D1330	13	3000	950	6	Energy Star listed	65 inc
10"	ASD-LFM-10D1340	13	4000	950	6	Energy Star listed	65 inc
11"	ASD-LFM-11D1530	15	3000	1,100	6	Energy Star listed	75 inc
11"	ASD-LFM-11D1540	15	4000	1,100	6	Energy Star listed	75 inc
13"	ASD-LFM-13D1830	18	3000	1,300	6	Energy Star listed	100 inc
13"	ASD-LFM-13D1840	18	4000	1,300	6	Energy Star listed	100 inc

Family	Size	Dimmable	Watts	CCT
ASD-LFM		D		
LED Flushmount	10 = 10"		13 = 13 W	30 = 3,000 K
	11 = 11"		15 = 15 W	40 = 4,000 K
	13 = 13"		18 = 18 W	

# LED Round Mini Panel

ASD LED round mini panels are a great choice for indoor lighting in residential and commercial environments. Our dimmable round panels have low energy consumption, long life and a low profile design. These ETL fixtures are Energy Star qualified and simple to install.



- Low energy consumption
- Easy to install
- Damp Location rated
- Dimmable with triac controls
- Finish: white
- Surface mount
- 5-year limited warranty - >54,000 Hrs

Image	Lighting Facts	ETL	Energy Star	Dimensions	Size	Model	Watts	CCT	Lm	Pcs in a case	Equivalency
					5"	ASD-MNPR-5D630-W	6	3,000	424	60	35W Inc
					5"	ASD-MNPR-5D640-W	6	4,000	424	60	35W Inc
					7"	ASD-MNPR-7D1230-W	12	3,000	889	40	100W Inc
					7"	ASD-MNPR-7D1240-W	12	4,000	889	40	100W Inc
					9"	ASD-MNPR-9D1830-W	18	3,000	1,341	20	150W Inc
					9"	ASD-MNPR-9D1840-W	18	4,000	1,341	20	150W Inc

Family	Size	Dimmable	Watts	CCT	Finish
<b>ASD-MNPR</b>		<b>D</b>			
LED Mini Panel Round	5 = 5"		6 = 6 W	30 = 3,000 K	W = White
	7 = 7"		12 = 12 W	40 = 4,000 K	
	9 = 9"		18 = 18 W		

# LED Retrofit Kit

ASD LED dimmable Recessed Retrofit Kits are the perfect upgrade for your existing recessed light fixture. We have 4" and 5"/6" kits available. These downlight retrofits are UL listed, Energy Star rated and suitable for damp location applications. Available in 2700 K and 4000 K color temperatures, our LED Recessed Retrofit kits are the perfect energy saving fixture for residential and commercial applications.



- Consumes up to 80% less energy
- Suitable for dry and damp locations
- Beam angle: 110°
- 5-year limited warranty

Image	Lighting Facts	ETL	Energy Star	FC	Dimensions	Size	Model	Watts	CCT	Lm	Pcs in a case	Equivalency
						4"	ASD-DL01D4-7.5W-27	7.5	2,700	525	6	50W Inc
						4"	ASD-DL01D4-7.5W-40	7.5	4,000	525	6	50W Inc
						6"	ASD-DL01D6-11.5W-27	11.5	2,700	747.5	6	65W Inc
						6"	ASD-DL01D6-11.5W-40	11.5	4,000	747.5	6	65W Inc
						6"	ASD-DL01D6-18W-27	18	2,700	1,170	6	85W Inc

Family	Modification	Dimmable	Size	Watts	CCT
<b>ASD-DL</b>	<b>I</b>	<b>D</b>			
LED Downlight			4 = 4"	7.5 = 7.5 W	27 = 2,700 K
			6 = 6"	11.5 = 11.5 W	40 = 4,000 K
				18 = 18 W	

## LED A19 Bulbs

ASD LED-A19 light bulbs provide beautiful, comfortable, warm light for your home. ASD Light bulbs were created with the homeowner in mind to produce natural looking, even light. These economically priced non-dimming bulbs provide many years of life; lowering power consumption while also decreasing your energy usage. These are perfect for table lamps, chandeliers, ceiling fans, and wall fixtures.


- Replaces up to a 60W incandescent bulb
- 10,000 hour LED Lifetime
- 2-year limited warranty



Family	Type	Non-dimmable	Base	Watts	CCT
ASD-LED	A19	N	26	5.5 = 5.5 W; 9 = 9 W	30 = 3,000 K; 40 = 4,000 K

Type	Model	Base	Watts	CCT	Lm	Pcs in a case	Equivalency
A19	ASD-LED-A19N26-5.5-30	26	5.5	3,000	450	100	40W Inc
A19	ASD-LED-A19N26-5.5-40	26	5.5	4,000	450	100	40W Inc
A19	ASD-LED-A19N26-9-30	26	9	3,000	800	100	60W Inc
A19	ASD-LED-A19N26-9-40	26	9	4,000	800	100	60W Inc



## LED-BR30 Dimmable Bulbs

ASD LED-BR30 Dimmable light bulbs produce better, brighter light than a traditional incandescent recessed light. Designed to enhance colors and produce a more natural feeling, these bulbs are your best value for the money. Our BR30 bulbs are designed for use in 6" recessed light cans and many years of life for a fraction of the cost of a traditional bulb.


- Replaces up to a 65W incandescent bulb
- 25,000 hour LED Lifetime
- 3-year limited warranty



Family	Type	Non-dimmable	Base	Watts	CCT
ASD-LED	BR30	N	26	10	30 = 3,000 K; 40 = 4,000 K

Type	Model	Base	Watts	CCT	Lm	Pcs in a case	Equivalency
BR30	ASD-LED-BR30D26-10-30	26	10	3,000	650	36	65W Inc
BR30	ASD-LED-BR30D26-10-40	26	10	4,000	650	36	65W Inc





®

**ASD Lighting Corp.**

120 Shawmut Rd, Canton, MA 02021


[www.asd-lighting.com](http://www.asd-lighting.com)

Phone: 781-739-3977 • Fax: 339-502-8970

[Orders@asd-lighting.com](mailto:Orders@asd-lighting.com)  
for orders and quotes

*New Standard  
in Lighting*

For orders, questions, or if you  
simply want to take us out for a beer,  
please call your local ASD representative:



**2017 / 2**

