

January 2017 Dallas Market



QUOIZEL.

Artisans in Lighting...since 1930



January 2017 Dallas Market

Photo Index..... 3 - 11

Quoizel Collections 12 - 21

Mini Collections..... 22 - 30

Dining & Foyer..... 31 - 37

Platinum Collection 38 - 50

Island Lights 51 - 52

Pendants 53 - 58

Mini Pendants 59 - 62

Semi-Flush Mounts 63 - 64

Wall Fixtures 65

Bath 66 - 73

Outdoor 74 - 96

Tiffany 97 - 101

Table & Floor 102

Mirrors 103 - 105

Corporate Headquarters

6 Corporate Parkway
Goose Creek, SC 29445
Phone: (843) 553-6700

**Corporate Headquarters
Customer Service**

590 Old Willets Path
Hauppauge, NY 11788
Phone: (631) 273-2700
Fax: (631) 231-7102
Toll-Free Consumer Hotline: (800) 645-5233

Showroom

Dallas Trade Mart

3rd Floor, Space 3200
Dallas, TX 75207
Phone: (214) 747-3665



TITLE 24 COMPLIANT ENERGY-EFFICIENT

- 13W, 18W or 23W Compact Fluorescent Included
- CFL Spring Self-Ballasted GU 24

To order Title 24 Compliant outdoor fixtures, please add "FL" to the end of any style number displaying this logo. (Medium base bulbs only)



DIFFUSER INCLUDED



DAMP LOCATION



WET LOCATION



MOUNTS AS UPLIGHT OR DOWNLIGHT



MOUNTS VERTICALLY OR HORIZONTALLY



DIMMERS:

Integrated Low Voltage LED Fixture – requires Electronic Low Voltage (ELV) dimmer.

Integrated 120v LED Fixture – C-L Dimmers recommended.

For more specific dimmer information, please contact: engineering@quozel.com.

WARRANTY:

Please refer to Quozel.com for complete warranty information.



Bulbs:

- Bulbs not included unless otherwise noted.
- Vintage Bulbs supplied are not necessarily the maximum wattage allowed.
- Products using LED and Halogen bulbs come with bulb(s) supplied in carton.
- Wattages stated are the maximum recommended; however, you may use lower wattages to suit your lighting needs.

LED:

- Integrated LED information chart provided wherever applicable.

Chain:

- (Single Tier) Chandelier, Dinette, Mini Chandeliers, Pendants, Mini Pendants and Island Lights come with 8' of wire and 4' of chain.
- (Two & Three Tier) Chandeliers and Foyer Fixtures come with 12' of wire and 8' of chain.
- All Outdoor Hanging Fixtures come with 12' of wire and 8' of chain.
- All Chain-Hung Mini Pendants come with 8' of wire and 4' of chain.

Other:

- All Rod-Hung Mini Pendants come with a minimum of 8' of wire.
- All Cord-Hung Mini Pendants come with a minimum of 8' of cord.
- All Cable-Hung Mini Pendants come with a minimum of 8' of cable.

Damp / Wet Locations:

- All flush and semi-flush mounted fixtures, bath fixtures and chandeliers are "Damp Location" listed.
- All outdoor hanging fixtures are "Damp Location" listed.
- All outdoor wall and post lights are "Wet Location" listed.

Electrical:

- All electrical fixtures are rated at 120-volt AC unless otherwise noted.
- Unless specified, all electrical fixtures are cUL or ETL listed.

Hardware:

- Backplate information and HCWO (Height from Center of Wall Opening) included for most wall fixtures (including outdoor) and bath fixtures.
- Canopy information included on almost all fixtures.
- All mirrors come with mounting hardware.

Tiffany / Naturals:

- Glass color in Tiffany lighting products vary in color. No two pieces are identical.
- Products that use natural materials are perfect for those seeking the aesthetics of natural variations. Due to its authenticity, the material may vary from pictured items.

Glass / Shades:

- Will appear darker when not illuminated.

In our efforts to constantly improve our products, changes may be made throughout the year that vary from printed information in the catalog.

Quoizel Collections

photo index



Dublin 12 - 16



Livery 17 - 19



Squire 20 - 21

Mini Collections

photo index



Aviary 22 - 24



Ceremony 25



Eons 26 - 27



Gallery 28 - 29



Holbeck 30

Dining & Foyer

photo index



Basin 31



Limelight 31



Alana 32 - 33



Jubilee 34



Gazebo 35



Siren 35



Dwelling 36



Lounge 36



Veranda 36



Chantelle 37



Warden 37

Platinum Collection

photo index



Infinity 38 - 40



Moonlit 41



Pipeline 41



Ballet 42



Identity 42



Pageant 43



Crystal Drape 44



Tower 44



Mystic 45



Amber Glow 46



Blaze 46




Embrace 47



Fleet 47



Beam 48



Emblem 49



Bracer 50



Glider 50

Island Lights

photo index



Aviary 51



Gallery 51



Caravan 52



Dwelling 52



Squire 52

Pendants

photo index



Brigade 53



Cityscape 53



Luxury 54



Gala 55



Titan 55



Gateway 56



Retreat 56



Taper 56

Pendants (continued)

photo index



Circuit 57



Glaze 57



Jive 58



Stadium 58

Mini Pendants

photo index



Luxury 59



Orion 59



Holbeck 60



Payson 60



Profile 60



Nob Hill 61



Rebound 61



Veil 61



Waterfall 61



Caster 62



Sanderson 62

Semi Flush

photo index



Cadet 63



Limelight 64



Basin 64



Emma 64



Taper 64

Wall Fixtures

photo index



Dublin 65



Livery 65



Warden 65

Bath

photo index



Westcap 66 - 67



Passage 68



Union 69



Meridian 70



Scholar 71



Tatum 72



Holland 73

Outdoor

photo index



Crusade 74 - 77



Newbury 78 - 81



Lighthouse 82 - 83



Carriage 84 - 85



Boardwalk 86 - 87



Everglade 88 - 89



Ravine 90 - 91



Terrace 92 - 93



Goldenrod 94 - 95



Beachside 96

Tiffany

photo index



Inglenook 97



Violets 98



Garland 99



Alcott 100



Legend 100



Sunrays 100



Blossom 100



Blue Trellis 101



Hummingbird 101



Meadow 101

Table & Floor

photo index



Broadway 102

Mirrors

photo index



Grace 103



Shoreline 103



Vanderbilt 103



Monarch 104



Artiste 104 - 105

DUBLIN

collection



The Dublin Collection is lighting for today's home. The pressed glass appears mesh-like both inside and out for a textured look and the Mystic Black finish highlights the industrial styling of the fixture.

FINISH: Mystic Black

GLASS: Pressed Clear

DAMP [DBN5009K](#)





DAMP **DBN5005K**

DAMP **DBN1506K**



DAMP **DBN5103K**

DUBLIN collection

ITEM	DIMENSIONS	CANOPY	BULBS
DBN1506K**	7.5" H, 6.5" W, 6.5" Dp.	.75" x 5"	1-100W Med. Base
DBN5005K	24" H, 26" W, 26" Dp.	.75" x 5"	5-100W Med. Base
DBN5009K*	30" H, 32" W, 32" Dp.	1.5" x 6.5"	9-100W Med. Base
DBN5103K**	32" H, 23.5" W, 23.5" Dp.	.75" x 5"	3-100W Med. Base

Fixtures come with 8' of wire and 4' of chain. *Fixture comes with 12' of wire and 8' of chain.
 **Comes with (2) 6" and (2) 12" Rods. Rod-hung fixtures come with 8' of wire.

DUBLIN

collection



DUBLIN

FINISH: Brushed Nickel

GLASS: Pressed Clear

DAMP

DBN5009BN





DUBLIN collection

ITEM	DIMENSIONS	CANOPY/BACKPLATE	HCWO	BULBS
DBN5005BN	24" H, 26" W, 26" Dp.	.75" x 5"		5-100W Med. Base
DBN5009BN*	30" H, 32" W, 32" Dp.	1.5" x 6.5"		9-100W Med. Base
DBN5103BN**	32" H, 23.5" W, 23.5" Dp.	.75" x 5"		3-100W Med. Base
DBN8701BN	10" H, 6.5" W, 8" Dp.	5" x 5"	5.5"	1-100W Med. Base

Fixtures come with 8' of wire and 4' of chain. *Fixture comes with 12' of wire and 8' of chain.
 **Comes with (2) 6" and (2) 12" Rods. Rod-hung fixtures come with 8' of wire.

DUBLIN

collection

DUBLIN

FINISH: Palladian Bronze

GLASS: Pressed Clear



DAMP

DBN8701PN



DAMP

DBN8602PN



DAMP

DBN8603PN



DAMP

DBN8604PN

DUBLIN

collection

ITEM	DIMENSIONS	CANOPY/BACKPLATE	HCWO	BULBS
DBN8602PN	9" H, 16" W, 8" Dp.	4.5" x 8"	5.5"	2-100W Med. Base
DBN8603PN	9" H, 25" W, 8" Dp.	4.5" x 8"	5.5"	3-100W Med. Base
DBN8604PN	9" H, 34.5" W, 8" Dp.	4.5" x 8"	5.5"	4-100W Med. Base
DBN8701PN	10" H, 6.5" W, 8" Dp.	5" x 5"	5.5"	1-100W Med. Base

DAMP LVY5009WT



LIVERY collection

ITEM

LVY5009WT

DIMENSIONS

37" H, 36" W, 36" Dp.

CANOPY

1" x 6"

BULBS

9-60W Cand. Base

LIVERY

collection



Beautifully appointed in cascading crystals, the Livery Collection is elegant and chic. The crystal-glass beads drape in a single strand that connect to a larger crystal, before splitting into two strands, creating a spectacular display of sparkle. The dark, rich Western Bronze finish is the ideal backdrop for this stunning design.

FINISH: Western Bronze



DAMP ■ [LUY8702WT](#)



DAMP ■ [LUY5005WT](#)



DAMP

LVY5004WT



DAMP

LVY2821WT

DAMP

LVY1716WT



LIVERY collection

ITEM	DIMENSIONS	CANOPY/BACKPLATE	HCWO	BULBS
LVY1716WT	17.5" H, 16.5" W, 16.5" Dp.	1" x 6"		3-60W Cand. Base
LVY2821WT	30" H, 21.5" W, 21.5" Dp.	1" x 6"		4-60W Cand. Base
LVY5004WT	22.5" H, 17.5" W, 17.5" Dp.	1" x 6"		4-60W Cand. Base
LVY5005WT	34" H, 28" W, 28" Dp.	1" x 6"		5-60W Cand. Base
LVY8702WT	18" H, 15.5" W, 9" Dp.	.75" x 5"	12.5"	2-60W Cand. Base

Fixtures come with 8' of wire and 4' of chain.

SQUIRE

collection



Shabby chic, industrial, rustic...the Squire Collection contains all of these elements in one, cohesive design. The fixture body is comprised of pipes and elbows finished in a Rustic Black which features an aged appearance. The beautiful clear glass mason jars are embellished with fruit-inspired designs that encase vintage-style bulbs completing the farmhouse style.

FINISH: Rustic Black

GLASS: Clear Mason Jars

Bulbs Shown Not Supplied



detail

DAMP [SQR1504RK](#)



DAMP [SQR5005RK](#)



Bulbs Shown Not Supplied

DAMP SQR538RK



DAMP SQR8701RK



DAMP SQR8602RK

MOUNTS



DAMP SQR8603RK

SQUIRE collection

ITEM	DIMENSIONS	CANOPY/BACKPLATE	HCW0	BULBS
SQR1504RK	9.5" H, 4.5" W, 4.5" Dp.	1" x 5"		1-100W Med. Base
SQR5005RK	23" H, 26" W, 26" Dp.	.75" x 5.125"		5-100W Med. Base
SQR538RK**	19.5" H, 38" W, 4.5" Dp.	1.5" x 12"		5-100W Med. Base
SQR8602RK	11" H, 14" W, 6" Dp.	4.75" x 6.5"	6"	2-100W Med. Base
SQR8603RK	11" H, 21.5" W, 6" Dp.	4.75" x 6.5"	6"	3-100W Med. Base
SQR8701RK	11.5" H, 5" W, 6" Dp.	4.75" x 6.5"	6"	1-100W Med. Base

Rod-Hung fixtures come with (2) 6" and (2) 12" Rods. *Comes with (4) 6" and (4) 12" Rods.
 Rod-Hung fixtures come with 8' of wire.

MINI collections

DAMP AVY5203PN



set of candle ivory sleeves included

With a clean, simplistic design that suits a variety of home décor styles, the Aviary Collection is classic style with a minimalist effect. The slender candle sleeves come in ivory for an elegant look but are also provided in rich Palladian Bronze to match the finish of this beautiful collection. This series is also available in a sleek Polished Nickel.

FINISH: PN - Palladian Bronze
PK - Polished Nickel

Aviary

DAMP AVY5206PN



DAMP AVY5204PN



AVIARY

mini collection



DAMP AVY5206PK



set of polished nickel candle sleeves included

Aviary



DAMP AVY5204PK



DAMP AVY5203PK

AVIARY

mini collection

ITEM	DIMENSIONS	CANOPY	BULBS
AVY5203PK/PN	17" H, 9.5" W, 9.5" Dp.	1" x 5"	3-60W Cand. Base
AVY5204PK/PN	23.5" H, 13" W, 13" Dp.	1" x 5"	4-60W Cand. Base
AVY5206PK/PN*	32" H, 20.5" W, 20.5" Dp.	1" x 5"	6-60W Cand. Base

Fixtures come with 8' of wire and 4' of chain. *Fixtures come with 12' of wire and 8' of chain.

AVIARY

mini clection

DAMP AVY654PN



Aviary

FINISH: PN - Palladian Bronze
PK - Polished Nickel



DAMP AVY654PK

AVIARY

mini clection

ITEM

AVY654PK/PN

DIMENSIONS

25.5" H, 54" W, 16.5" Dp.

CANOPY

1" x 25.5"

BULBS

6-60W Cand. Base

CEREMONY

mini collection

An elegantly designed collection, Ceremony combines traditional and contemporary elements harmoniously. The fixture body is finished in rich Palladian Bronze and is accented with crystal-glass balls and candle holders for a sleek look.

FINISH: Palladian Bronze
SHADE: Light Amber Organza



Ceremony

CEREMONY

mini collection

ITEM	DIMENSIONS	CANOPY	BULBS	SHADE DIMS
CRY1716PN	11.5" H, 16" W, 16" Dp.	.75" x 6"	3-60W Cand. Base	(14" x 14") x (16" x 16") x 6.75"
CRY5005PN	15.5" H, 25" W, 25" Dp.	.75" x 6"	5-60W Cand. Base	(7" x 23.5") x (23.5" x 25") x 25"
CRY5006PN	14" H, 28" W, 28" Dp.	.75" x 6"	6-60W Cand. Base	
CRY5009PN	20.5" H, 32" W, 32" Dp.	.75" x 6"	9-60W Cand. Base	

Fixtures come with 8' of wire and 4' of chain. Rod-hung fixtures come with (2) 6" and (2) 12" Rods.

EONS

mini collection

The circle is a symbol of eternity, a perfect design suited for the Eons Collection. The overlapping bands intersect beautifully and can be adjusted subtly to suit your preference. The rich Western Bronze on the fixture body is accented with a brass finish on the candle sleeves furthering its elegant style.

FINISH: Western Bronze

Eons

DAMP

EON5009WT





DAMP ■ **EON1715WT**



DAMP ■ **EON2823WT**



DAMP ■ **EON5006WT**

Eons

EONS mini collection

ITEM	DIMENSIONS	CANOPY	BULBS
EON1715WT**	14.5" H, 15" W, 15" Dp.	1.5" x 6"	4-60W Cand. Base
EON2823WT	23" H, 23" W, 23" Dp.	1.5" x 6"	5-60W Cand. Base
EON5006WT*	32" H, 26" W, 26" Dp.	1.5" x 6"	6-60W Cand. Base
EON5009WT*	43" H, 32" W, 32" Dp.	1.5" x 6"	9-60W Cand. Base

Rod-hung fixtures come with (2) 6" and (2) 12" Rods. *Fixtures come with 12' of wire and 8' of chain.
 **Converts into a pendant.

GALLERY

mini collection

Gallery

With a clean, simplistic design that is traditional in theme yet suits a variety of décors, the Gallery Collection is classic with a minimalistic effect. The slender candle sleeves come in ivory for an elegant look but are also provided in Royal Ebony to match the finish of this beautiful collection.

FINISH: Royal Ebony



DAMP

GLY648BA



DAMP

GLY5203BA



set of royal ebony candle sleeves included

Gallery

DAMP

GLY5204BA



DAMP

GLY5206BA



GALLERY mini collection

ITEM	DIMENSIONS	CANOPY	BULBS
GLY5203BA	15" H, 10" W, 10" Dp.	.75" x 5.5"	3-60W Cand. Base
GLY5204BA	20" H, 14" W, 14" Dp.	.75" x 5.5"	4-60W Cand. Base
GLY5206BA	30" H, 22" W, 22" Dp.	.75" x 5.5"	6-60W Cand. Base
GLY648BA	25.5" H, 48" W, 18" Dp.	.75" x 17.25"	6-60W Cand. Base

Fixture comes with 8' of wire and 4' of chain. . *Fixture comes with 12' of wire and 8' of chain.

HOLBECK

mini collection

The Holbeck Collection is comprised of wood and metal in a great display of harmonious design. The chocolate-hued finish of the wood arms is accented with the Brushed Nickel metal elements of the fixture body. The clear seedy glass shades allow maximum light and proudly display the vintage-style filament bulbs.

FINISH: Brushed Nickel

GLASS: Clear Seedy

DAMP HE5009BN



DAMP HE1505BN

Holbeck



Bulbs Shown Not Supplied

DAMP HE5005BN



DAMP HE5003BN



HOLBECK

mini collection

ITEM	DIMENSIONS	CANOPY	BULBS
HE1505BN	10.5" H, 5" W, 5" Dp.	1.5" x 5.5"	1-100W Med. Base
HE5003BN	20.5" H, 19" W, 19" Dp.	1.5" x 5.5"	3-100W Med. Base
HE5005BN	26.5" H, 27" W, 27" Dp.	1.5" x 5.5"	5-100W Med. Base
HE5009BN*	34" H, 31" W, 31" Dp.	1.5" x 5.5"	9-100W Med. Base

DAMP LMT5009PN



Limelight

FINISH: Palladian Bronze

**See matching semi-flush pg. 58*

DAMP LMT5012PN



DAMP BSN5006EK



Basin

FINISH: Earth Black

**See matching semi-flush pg. 64*

Bulbs Shown Not Supplied

ITEM	DIMENSIONS	CANOPY	BULBS
BSN5006EK	30.5" H, 25" W, 25" Dp.	.75" x 6"	6-100W Med. Base
LMT5009PN*	24" H, 24" W, 24" Dp.	.75" x 5"	9-60W Vintage Bulbs Supplied
LMT5012PN*	24" H, 28" W, 28" Dp.	.75" x 5"	12-60W Vintage Bulbs Supplied

Fixtures come with 8' of wire and 4' of chain. MAX WATTAGE: 100W Med. Base

FINISH: Mystic Black

Alana

DAMP ANA5005K



DAMP ANA5015K





DAMP **ANA5009K**



removable crystal candle sleeve covers

crystal candle sleeve covers →



DAMP **ANA5008K**

ALANA

ITEM	DIMENSIONS	CANOPY	BULBS
ANA5005K	24.5" H, 23.5" W, 23.5" Dp.	.75" x 5.5"	5-60W Cand. Base
ANA5008K	30" H, 30" W, 30" Dp.	.75" x 5.5"	8-60W Cand. Base
ANA5009K*	31.5" H, 32" W, 32" Dp.	.75" x 5.5"	9-60W Cand. Base
ANA5015K*	43" H, 41" W, 41" Dp.	.75" x 5.5"	15-60W Cand. Base

Fixtures come with 8' of wire and 4' of chain. *Fixtures come with 12' of wire and 8' of chain.

DINING & FOYER

Jubilee

FINISH: Mystic Black

SHADE: Metal with Glass Circles



DAMP [JBE5208K](#)



DAMP [JBE2822K](#)



DAMP [JBE5204K](#)

ITEM

DIMENSIONS

CANOPY

BULBS

JBE2822K

8" H, 22" W, 22" Dp.

.75" x 5.5"

4-100W Med. Base

JBE5204K

23" H, 16" W, 16" Dp.

.78" x 5.5"

4-60W Cand. Base

JBE5208K

31" H, 22" W, 22" Dp.

.75" x 5.5"

8-60W Cand. Base



DAMP ■ **GZ5104GK**

Gazebo

FINISH: Grey Ash

GLASS: Clear Seedy



DAMP ■ **SRN5208MK**



DAMP ■ **SRN5204MK**

Siren

FINISH: Mercado Black


ITEM	DIMENSIONS	CANOPY	BULBS
GZ5204GK	28.5" H, 17" W, 17" Dp.	.875 x 5"	4-60W Cand. Base
SRN5204MK	24.5" H, 21" W, 21" Dp.	1.5" x 5.5"	4-60W Cand. Base
SRN5208MK	32.5" H, 28" W, 28" Dp.	1.5" x 5.5"	8-60W Cand. Base

DINING & FOYER

QUOIZEL
NATURALS
WOOD

Veranda

FINISH: Western Bronze




DAMP

VRA5204WT

Dwelling

FINISH: Western Bronze

**See matching island light pg. 52*



DAMP

DWL5204WT

Lounge

FINISH: Grey Ash

GLASS: Clear Seedy



DAMP

LGE5005GK

ITEM

DIMENSIONS

CANOPY

BULBS

DWL5204WT

21.5" H, 15" W, 15" Dp.

.75" x 5.5"

4-60W Cand. Base

LGE5005GK

24.5" H, 27.5" W, 27.5" Dp.

.75" x 5"

5-60W Cand. Base

VRA5204WT

29" H, 16" W, 16" Dp.

.875" x 5.5"

4-60W Cand. Base

Warden

FINISH: Western Bronze

SHADE: Light Beige Fabric

DAMP **WDN5004WT**

**See matching wall fixture pg. 65*

crystal accents



DAMP **CNT5204VG**

Chantelle

FINISH: Vintage Gold

crystal drops



DAMP **CNT5005VG**



ITEM	DIMENSIONS	CANOPY	BULBS
CNT5204VG	35" H, 20.5" W, 20.5" Dp.	1" x 5"	4-60W Cand. Base
CNT5005VG	24.5" H, 28" W, 28" Dp.	1" x 5"	5-60W Cand. Base
WDN5004WT	24.5" H, 27" W, 27" Dp.	.75" x 6"	4-60W Cand. Base

PLATINUM

collection

FINISH: Polished Chrome

SHADE: Crystal Studded

DAMP

PCIN1716C



Infinity

INTEGRATED LED
10 YEAR WARRANTY

LED CHART

Lumens	2,200
Total Watts	22W
Color Rendering Index (CRI)	90
Color Temperature (CCT)	3000K
Dimmable	YES



DAMP

PCIN1828C



INTEGRATED LED
10 YEAR WARRANTY

LED CHART

Lumens	3,200 + 1,600
Total Watts	32W + 16W
Color Rendering Index (CRI)	90
Color Temperature (CCT)	3000K
Dimmable	YES

ITEM

DIMENSIONS

CANOPY

LIGHT SOURCE

PCIN1716C

6" H, 16.5" W, 16.5" Dp.

1.5" x 13.75"

See Chart for LED Information

PCIN1828C

10.5" H, 27.5" W, 27.5" Dp.

1.75" x 10"

See Chart for LED Information



DAMP

PCIN540C

INTEGRATED LED
10 YEAR WARRANTY

LED CHART

Lumens	1,350
Total Watts	13.5W
Color Rendering Index (CRI)	90
Color Temperature (CCT)	3000K
Dimmable	YES

Infinity

PLATINUM
by QUOIZEL
CRYSTAL ♦ COLLECTION

DAMP

PCIN1504C

INTEGRATED LED
10 YEAR WARRANTY

LED CHART

Lumens	450
Total Watts	4.5W
Color Rendering Index (CRI)	90
Color Temperature (CCT)	3000K
Dimmable	YES



INFINITY

ITEM	DIMENSIONS	CANOPY	LIGHT SOURCE
PCIN1504C	11" H, 4" W, 4" Dp.	1.5" x 5"	See Chart for LED Information
PCIN540C	11" H, 31.5" W, 4" Dp.	4.75" x 4.75"	See Chart for LED Information

PLATINUM

collection

FINISH: Polished Chrome


SHADE: Crystal Studded

Infinity

DAMP

PCIN8518C

INTEGRATED **LED**
10 YEAR WARRANTY



Lumens	800
Total Watts	8W
Color Rendering Index (CRI)	90
Color Temperature (CCT)	3000K
Dimmable	YES

PLATINUM
by QUOIZEL
CRYSTAL ♦ COLLECTION

INTEGRATED **LED**
10 YEAR WARRANTY



DAMP

PCIN8527C

Lumens	1,200
Total Watts	12W
Color Rendering Index (CRI)	90
Color Temperature (CCT)	3000K
Dimmable	YES

INTEGRATED **LED**
10 YEAR WARRANTY

LED CHART

Lumens	1,600
Total Watts	16W
Color Rendering Index (CRI)	90
Color Temperature (CCT)	3000K
Dimmable	YES



DAMP

PCIN8536C

INFINITY

ITEM	DIMENSIONS	CANOPY/BACKPLATE	HCWO	BULBS
PCIN8518C	5" H, 18" W, 4.5" Dp.	4.75" x 4.75"	9.13"	See Chart for LED Information
PCIN8527C	5" H, 27.5" W, 4.5" Dp.	4.75" x 4.75"	13.88"	See Chart for LED Information
PCIN8536C	5" H, 35.5" W, 4.5" Dp.	4.75" x 4.75"	17.75"	See Chart for LED Information

Moonlit

FINISH: C - Polished Chrome
W - White

GLASS: Clear Panel with Acrylic Beads



DAMP

PCMT1614C



DAMP

PCMT1614W

INTEGRATED LED
10 YEAR WARRANTY

LED CHART

Lumens	1,500
Total Watts	15W
Color Rendering Index (CRI)	90
Color Temperature (CCT)	3000K
Dimmable	YES



DAMP

PCPN2816PK

DAMP

PCPN832PK



detail

Pipeline

FINISH: Polished Nickel

SHADE: Metal & Etched Glass Pipes

ITEM	DIMENSIONS	CANOPY	BULBS
PCMT1614C	2.5" H, 14" W, 14" Dp.	2" x 11"	See Chart for LED Information
PCMT1614W	2.5" H, 14" W, 14" Dp.	2" x 11"	See Chart for LED Information
PCPN2816PK	12" H, 16.5" W, 16.5" Dp.	1" x 4.75"	5-40W Clear G9 Xenon Supplied
PCPN832PK	12" H, 32" W, 13" Dp.	1" x 17.75"	8-40W Clear G9 Xenon Supplied

Cord hung fixtures come with 8' of cord.

PLATINUM

collection

Ballet

FINISH: Brushed Nickel
SHADE: Clear Faceted Crystals

DAMP **PCBL2817BN**



convertible

DAMP **PCBL2821BN**



hanging crystals →

DAMP **PCBL1614BN**



Identity

FINISH: Polished Chrome
SHADE: Crystal Studded

PLATINUM
 by QUOIZEL
 CRYSTAL ♦ COLLECTION

DAMP **PCIT1612C**



DAMP **PCIT1616C**



ITEM	DIMENSIONS	CANOPY	BULBS
PCBL1614BN	8" H, 13.5" W, 13.5" Dp.	.75" x 10"	2-100W Med. Base
PCBL2817BN	12.5" H, 16.5" W, 16.5" Dp.	.75" x 5"	4-60W Cand. Base
PCBL2821BN	13" H, 20.5" W, 20.5" Dp.	.75" x 5"	5-60W Cand. Base
PCIT1612C	6" H, 11.5" W, 11.5" Dp.	1" x 10"	4-40W Clear G9 Xenon Supplied
PCIT1616C	7.5" H, 16" W, 16" Dp.	1.75" x 13.75"	6-40W Clear G9 Xenon Supplied



detail

Pageant

FINISH: Polished Chrome



PCPG2816C



PCPG2824C

ITEM	DIMENSIONS	CANOPY	BULBS
PCPG2816C	16.5" H, 16" W, 16" Dp.	1" x 4.75"	4-40W G9 Xenon or G9 LED
PCPG2824C	23.5" H, 23.5" W, 23.5" Dp.	1" x 4.75"	6-40W G9 Xenon or G9 LED

PLATINUM

collection

Tower

DAMP PCTE1616C



FINISH: Polished Chrome

SHADE: Clear Crystal Faceted Drops

DAMP PCTE1610C



PLATINUM
by QUOIZEL

Crystal Drape

FINISH: Polished Chrome

SHADE: Clear Crystal Drops



DAMP PCCD1613C



DAMP PCCD1615C

ITEM

DIMENSIONS

CANOPY

BULBS

PCCD1613C	10" H, 12.5" W, 12.5" Dp.	1" x 11.75"	4-40W Clear G9 Xenon Supplied
PCCD1615C	11.5" H, 15" W, 15" Dp.	1" x 13.75"	5-40W Clear G9 Xenon Supplied
PCTE1610C	10.5" H, 10" W, 10" Dp.	1" x 10"	3-40W Clear G9 Xenon Supplied
PCTE1616C	14" H, 16" W, 16" Dp.	1" x 13.75"	5-40W Clear G9 Xenon Supplied



Mystic

FINISH: Polished Chrome

SHADE: Outer: Metal Laser Cut
Inner: Silver Organza on White Hardback



 **PCMC2816C**

 **PCMC2820C**



convertible

ITEM	DIMENSIONS	CANOPY	BULBS
PCMC2816C	6" H, 16" W, 16" Dp.	1" x 6"	3-100W Med. Base
PCMC2820C	7.5" H, 20" W, 20" Dp.	1" x 6"	4-100W Med. Base

PLATINUM

collection

Amber Glow

FINISH: Polished Chrome

SHADE: Metal Inlay with Clear Crystal Beads

INTEGRATED LED
10 YEAR WARRANTY



DAMP

PCAB1614C

LED CHART

Lumens	1,760
Total Watts	17.6W
Color Rendering Index (CRI)	90
Color Temperature (CCT)	3000K
Dimmable	YES



PLATINUM
by QUOIZEL

Blaze

FINISH: Polished Chrome

DAMP

PCBZ1716C



INTEGRATED LED
10 YEAR WARRANTY

LED CHART

Lumens	2,200
Total Watts	22W
Color Rendering Index (CRI)	90
Color Temperature (CCT)	3000K
Dimmable	YES



DAMP

PCBZ1712C

INTEGRATED LED
10 YEAR WARRANTY

LED CHART

Lumens	1,700
Total Watts	17W
Color Rendering Index (CRI)	90
Color Temperature (CCT)	3000K
Dimmable	YES



detail

ITEM

DIMENSIONS

CANOPY

BULBS

PCAB1614C	4.5" H, 14.5" W, 14.5" Dp.	1.5" x 11.75"	See Chart for LED Information
PCBZ1712C	2.5" H, 12" W, 12" Dp.	2" x 11"	See Chart for LED Information
PCBZ1716C	3" H, 16" W, 16" Dp.	2.5" x 15"	See Chart for LED Information

INTEGRATED LED
10 YEAR WARRANTY

LED CHART

Lumens	2,700
Total Watts	27W
Color Rendering Index (CRI)	90
Color Temperature (CCT)	3000K
Dimmable	YES

DAMP **PCEM1619C**



Embrace

FINISH: Polished Chrome

GLASS: Clear Faceted Crystals

PLATINUM
by QUOIZEL



DAMP **PCFL8522C**

INTEGRATED LED
10 YEAR WARRANTY

LED CHART

Lumens	2,991.37
Total Watts	40.4W
Color Rendering Index (CRI)	90
Color Temperature (CCT)	3000K
Dimmable	YES

Fleet

FINISH: Polished Chrome

SHADE: Opal Etched

INTEGRATED LED
10 YEAR WARRANTY

LED CHART

Lumens	3,947.42
Total Watts	54W
Color Rendering Index (CRI)	90
Color Temperature (CCT)	3000K
Dimmable	YES

DAMP **PCFL8531C**



MOUNTS

ITEM	DIMENSIONS	CANOPY/BACKPLATE	HCW0	BULBS
PCEM1619C	4.5" H, 18" W, 18" Dp.	2" x 15.75"		See Chart for LED Information
PCFL8522C	5" H, 22.5" W, 4" Dp.	4.75" x 6.75"	11.25"	See Chart for LED Information
PCFL8531C	5" H, 30.5" W, 4" Dp.	4.75" x 6.75"	15.25"	See Chart for LED Information

PLATINUM

collection



INTEGRATED LED
10 YEAR WARRANTY

DAMP PCBB8520C

LED CHART

Lumens	1,800
Total Watts	23W
Color Rendering Index (CRI)	90
Color Temperature (CCT)	3000K
Dimmable	YES

PLATINUM
by QUOIZEL



DAMP PCBB8526C

INTEGRATED LED
10 YEAR WARRANTY

LED CHART

Lumens	2,400
Total Watts	31W
Color Rendering Index (CRI)	90
Color Temperature (CCT)	3000K
Dimmable	YES

Beam

FINISH: Polished Chrome

SHADE: Acrylic



INTEGRATED LED
10 YEAR WARRANTY

DAMP PCBB8532C

LED CHART

Lumens	3,000
Total Watts	38.5W
Color Rendering Index (CRI)	90
Color Temperature (CCT)	3000K
Dimmable	YES

ITEM	DIMENSIONS	BACKPLATE	HCWO	BULBS
PCBB8520C	5" H, 20" W, 2" Dp.	5" x 7"	9"	See Chart for LED Information
PCBB8526C	5" H, 26" W, 2" Dp.	5" x 7"	12"	See Chart for LED Information
PCBB8532C	5.5" H, 32" W, 2" Dp.	5.25" x 7.25"	15"	See Chart for LED Information



INTEGRATED LED
10 YEAR WARRANTY

LED CHART

Lumens	1,800
Total Watts	23W
Color Rendering Index (CRI)	90
Color Temperature (CCT)	3000K
Dimmable	YES

DAMP

PCEB8518C



INTEGRATED LED
10 YEAR WARRANTY

LED CHART

Lumens	2,400
Total Watts	31W
Color Rendering Index (CRI)	90
Color Temperature (CCT)	3000K
Dimmable	YES

DAMP

PCEB8524C

Emblem

FINISH: Polished Chrome

SHADE: Acrylic



INTEGRATED LED
10 YEAR WARRANTY

LED CHART

Lumens	3,000
Total Watts	38.5W
Color Rendering Index (CRI)	90
Color Temperature (CCT)	3000K
Dimmable	YES

DAMP

PCEB8530C

ITEM	DIMENSIONS	BACKPLATE	HCW0	BULBS
PCEB8518C	5" H, 18" W, 2" Dp.	5" x 5"	9"	See Chart for LED Information
PCEB8524C	5" H, 24" W, 2" Dp.	5" x 5"	12"	See Chart for LED Information
PCEB8530C	5.5" H, 30" W, 2" Dp.	5.25" x 5.25"	15"	See Chart for LED Information

PLATINUM

collection


DAMP

PCGD8522C

INTEGRATED LED
10 YEAR WARRANTY

LED CHART

Lumens	1,729
Total Watts	29W
Color Rendering Index (CRI)	90
Color Temperature (CCT)	3000K
Dimmable	YES



Glider

FINISH: Polished Chrome

SHADE: Acrylic

INTEGRATED LED
10 YEAR WARRANTY

DAMP

PCGD8531C

LED CHART

Lumens	2,423
Total Watts	40.2W
Color Rendering Index (CRI)	90
Color Temperature (CCT)	3000K
Dimmable	YES

PLATINUM
by QUOIZEL

INTEGRATED LED
10 YEAR WARRANTY


LED CHART

Lumens	1,251
Total Watts	20.3W
Color Rendering Index (CRI)	90
Color Temperature (CCT)	3000K
Dimmable	YES



DAMP

PCBC8518C



Bracer

FINISH: Polished Chrome

SHADE: Acrylic

DAMP

PCBC8526C

INTEGRATED LED
10 YEAR WARRANTY

LED CHART

Lumens	1,899
Total Watts	32.4W
Color Rendering Index (CRI)	90
Color Temperature (CCT)	3000K
Dimmable	YES

ITEM

DIMENSIONS

BACKPLATE

HCWO

BULBS

PCBC8518C	5" H, 18" W, 4" Dp.	4.75" x 6.75"	9"	See Chart for LED Information
PCBC8526C	5" H, 26" W, 4" Dp.	4.75" x 6.75"	13"	See Chart for LED Information
PCGD8522C	5" H, 22" W, 3.5" Dp.	5" x 7"	11"	See Chart for LED Information
PCGD8531C	5" H, 31" W, 3.5" Dp.	5" x 7"	15.5"	See Chart for LED Information

ISLAND LIGHTS



DAMP AVY654PN

Aviary

FINISH: PN - Palladian Bronze
PK - Polished Nickel

**See matching chandeliers pgs. 22 - 23*



DAMP AVY654PK



DAMP GLY648BA

Gallery

FINISH: Royal Ebony



set of royal ebony candle sleeves included

**See matching chandeliers pg. 29*

ITEM	DIMENSIONS	CANOPY	BULBS
AVY654PK/PN*	25.5" H, 54" W, 16.5" Dp.	1" x 25.5"	6-60W Cand. Base
GLY648BA*	25.5" H, 48" W, 18" Dp.	.75" x 17.5"	6-60W Cand. Base

ISLAND LIGHTS

**See matching collection pgs. 20 - 21*

Squire

FINISH: Rustic Black
GLASS: Clear Mason Jars

Bulbs Shown Not Supplied

DAMP

SQR538RK



DAMP

CRV536WT

Caravan

FINISH: Western Bronze
GLASS: Clear Hammered

Bulbs Shown Not Supplied



**See matching chandeliers pg. 36*

QUOIZEL
NATURALS
WOOD

Dwelling

FINISH: Western Bronze

DAMP

DWL540WT



ITEM

DIMENSIONS

CANOPY

BULBS

CRV536WT**

14" H, 36" W, 13" Dp.

.75" x 12"

5-100W Med. Base

DWL540WT*

15" H, 40" W, 12" Dp.

1" x 12"

5-60W Cand. Base

SQR538RK**

19.5" H, 38" W, 4.5" Dp.

1.5" x 12"

5-100W Med. Base

PENDANTS



convertible

DAMP

BGE2822AP



Brigade

FINISH: AP - Antique Polished Nickel
WT - Western Bronze

SHADE: Outer: Metal Laser Cut
Inner - AP: White Fabric
Inner - WT: Off-White Fabric



convertible

DAMP

BGE2822WT



convertible

DAMP

CTS2822PK



Cityscape

FINISH: PK - Polished Nickel
WT - Western Bronze

SHADE: Metal Mesh



convertible

DAMP

CTS2822WT



Bulbs Shown Not Supplied

ITEM	DIMENSIONS	CANOPY	BULBS	SHADE DIMS
BGE2822AP	6.5" H, 22" W, 22" Dp.	.88" x 4.75"	4-100W Med. Base	(5.5" x 18") x (18" x 18") x 18"
BGE2822WT	6.5" H, 22" W, 22" Dp.	.88" x 4.75"	4-100W Med. Base	(5.5" x 18") x (18" x 18") x 18"
CTS2822PK	11" H, 22" W, 22" Dp.	5"	5-60W Cand. Base	(6.5" x 22") x (22" x 22") x 22"
CTS2822WT	11" H, 22" W, 22" Dp.	5"	5-60W Cand. Base	(6.5" x 22") x (22" x 22") x 22"

PENDANTS



all convertible



LXY2822IB



LXY2817IB



**See matching
mini pendant pg. 53*

Luxury

FINISH: IB - Imperial Bronze
VG - Vintage Gold

SHADE: Metal with Square Crystals



LXY2817VG



LXY2822VG



all convertible



ITEM

DIMENSIONS

CANOPY

BULBS

LXY2817IB

8" H, 17.5" W, 17.5" Dp.

.75" x 5.5"

4-100W Med. Base

LXY2817VG

8" H, 17.5" W, 17.5" Dp.

.75" x 5.5"

4-100W Med. Base

LXY2822IB

8" H, 22" W, 22" Dp.

.75" x 5.5"

5-100W Med. Base

LXY2822VG

8" H, 22" W, 22" Dp.

.75" x 5.5"

5-100W Med. Base

Gala

FINISH: Vino Bronze



DAMP **GLA2816VZ**



DAMP **GLA2824VZ**

DAMP **TTA2824K**



Titan

FINISH: Mystic Black



DAMP **TTA2817K**

ITEM	DIMENSIONS	CANOPY	BULBS
GLA2816VZ	12.5" H, 16.5" W, 16.5" Dp.	.75" x 5.5"	3-100W Med. Base
GLA2824VZ	18" H, 23.5" W, 23.5" Dp.	.75" x 5.5"	6-100W Med. Base
TTA2817K	17.5" H, 17" W, 17" Dp.	.75" x 5"	4-60W Cand. Base
TTA2824K	25" H, 24" W, 24" Dp.	.75" x 5"	5-60W Cand. Base

Rod-hung fixtures come with (2) 6" and (2) 12" Rods.

PENDANTS

Taper

FINISH: Polished Chrome

SHADE: Off White Fabric

**See matching semi-flush pg. 64*

 **DAMP** **TPR2823C**



 **DAMP** **TPR2816C**




Gateway

FINISH: Mystic Black

SHADE: Inner: White Linen Fabric
Outer: Open Metal Pattern with Silver Balls in Center

 **DAMP** **QF2773K**



convertible

 **DAMP** **QF2782DC**

QUOIZEL
NATURALS
RATTAN

convertible



Retreat

FINISH: Dark Cherry

SHADE: Inner: Off White Hardback Fabric
Outer: Rattan

ITEM	DIMENSIONS	CANOPY	BULBS	SHADE DIMS
QF2773K	9.5" H, 20" W, 20" Dp.	0.875 x 5.5"	4-100W Med. Base	(7.5" x 16.5") x (16.5" x 16.5") x 16.5"
QF2782DC	10.5" H, 21.5" W, 21.5" Dp.	1.5" x 5"	4-100W Med. Base	(8.5" x 16.5") x (16.5" x 16.5") x 16.5"
TPR2816C	19" H, 16" W, 16" Dp.	.87" x 4.75"	3-100W Med. Base	(4.75" x 16") x (16" x 14.5") x 14.5"
TPR2823C	25" H, 23" W, 23" Dp.	.87" x 4.75"	4-100W Med. Base	(6.37" x 22.75") x (22.75" x 20.5") x 20.5"

DAMP

CCT2830WT



Glaze

FINISH: Polished Chrome

GLASS: Clear Panels



detail



convertible

DAMP

QF2783C



Circuit

FINISH: Western Bronze

Bulbs Shown Not Supplied



DAMP

CCT2824WT



all convertible

DAMP

CCT2814WT

ITEM	DIMENSIONS	CANOPY	BULBS
CCT2814WT	15" H, 14" W, 14" Dp.	1" x 5.5"	1-100W Med Base
CCT2824WT	25" H, 24" W, 24" Dp.	1" x 5.5"	5-100W Med. Base
CCT2830WT	31" H, 30" W, 30" Dp.	1" x 5.5"	6-100W Med. Base
QF2783C	10.5" H, 23.5" W, 23.5" Dp.	.75" x 5"	5-100W Med. Base

PENDANTS

Stadium

FINISH: Mystic Black

SHADE: Open Metal Circles

DAMP

SDM2814K



convertible



DAMP

SDM2824K



Artistry

FINISH: Vintage Gold

SHADE: Metal with Clear Glass Accents

DAMP

QF2787VG



ITEM

DIMENSIONS

CANOPY

BULBS

QF2787VG

15" H, 14" W, 14" Dp.

.75" x 5"

4-60W Cand. Base

SDM2814K

14" H, 14" W, 14" Dp.

1" x 5"

3-60W Cand. Base

SDM2824K

22.5" H, 24" W, 24" Dp.

1" x 6"

6-60W Cand. Base

MINI PENDANTS

Luxury

FINISH: IB - Imperial Bronze
VG - Vintage Gold

SHADE: Metal with Square Crystals

**See matching
pendants pg. 48*



DAMP LXY1506VG



DAMP LXY1506IB



DAMP ON1509WT

Orion

FINISH: BN - Brushed Nickel
WT - Western Bronze



DAMP ON1509BN

ITEM	DIMENSIONS	CANOPY	BULBS
LXY1506IB	7.5" H, 6.5" W, 6.5" Dp.	.75" x 5.5"	1-100W Med. Base
LXY1506VG	7.5" H, 6.5" W, 6.5" Dp.	.75" x 5.5"	1-100W Med. Base
ON1509BN	9" H, 9" W, 9" Dp.	.75" x 5"	1-100W Med. Base
ON1509WT	9" H, 9" W, 9" Dp.	.75" x 5"	1-100W Med. Base

Rod-hung fixtures come with (2) 6" and (2) 12" Rods.

MINI PENDANTS

Bulbs Shown Not Supplied



Profile

FINISH: Mystic Black
GLASS: Light Grey Blown

DAMP **QPP2818K**



detail

Payson

FINISH: Brushed Nickel
GLASS: Clear Seedy


DAMP **QPP2781BN**

Holbeck

FINISH: Brushed Nickel
GLASS: Clear Seedy

**See matching chandeliers pg. 30*

DAMP **HE1505BN**



ITEM	DIMENSIONS	CANOPY	BULBS
HE1505BN	10.5" H, 5" W, 5" Dp.	1.5" x 5.5"	1-100W Med. Base
QPP2781BN	12" H, 6.5" W, 6" Dp.	.75" x 5.5"	1-100W Med. Base
QPP2818K	12.5" H, 10" W, 10" Dp.	.75" x 5"	1-100W Med. Base

DAMP **QPP2790K**

Veil

FINISH: Mystic Black
GLASS: Clear Smoke Hammered Blown



detail



DAMP **QPP2784C**

Rebound

FINISH: Polished Chrome
GLASS: Clear Ribbed

Bulbs Shown Not Supplied



Nob Hill

FINISH: Brushed Nickel
GLASS: Clear Hammered Blown

DAMP **QPP2816BN**



Waterfall

FINISH: Polished Chrome
GLASS: Clear Water

DAMP **QPP2785C**

ITEM	DIMENSIONS	CANOPY	BULBS
QPP2784C	16.5" H, 9" W, 9" Dp.	1" x 4.75"	1-100W Med. Base
QPP2785C	17" H, 10.5" W, 10.5" Dp.	1" x 4.75"	1-100W Med. Base
QPP2790K	10.5" H, 7.5" W, 7.5" Dp.	.75" x 5"	1-100W Med. Base
QPP2816BN	13.5" H, 6.5" W, 6.5" Dp.	.75" x 5"	1-100W Med. Base

MINI PENDANTS



detail

Bulbs Shown Not Supplied

Caster

FINISH: Mystic Black

GLASS: QPP2788K
Light Brown Hammered Blown
with Brass Band
QPP2789K
Recycled Light Blue Hammered
Blown with Brass Band



DAMP — **QPP2788K**



DAMP — **QPP2789K**

Sanderson

FINISH: Polished Chrome
GLASS: Clear Sand



DAMP — **QPP2817K**

ITEM	DIMENSIONS	CANOPY	BULBS
QPP2788K	12" H, 8" W, 8" Dp.	.75" x 5"	1-100W Med. Base
QPP2789K	11.5" H, 6" W, 6" Dp.	.75" x 5"	1-100W Med. Base
QPP2817K	9.5" H, 13.5" W, 13.5" Dp.	.75" x 5"	1-100W Med. Base

SEMI FLUSH



DAMP CDT1719BN



DAMP CDT1719OZ



DAMP CDT1715OZ



DAMP CDT1715BN

Cadet
FINISH: BN - Brushed Nickel
 OZ - Old Bronze
GLASS: White Painted

ITEM	DIMENSIONS	CANOPY	BULBS	SHADE DIMS
CDT1715BN	10" H, 15" W, 15" Dp.	1.5" x 6.5"	3-100W Med. Base	
CDT1715OZ	10" H, 15" W, 15" Dp.	1.5" x 6.5"	3-100W Med. Base	
CDT1719BN	10.5" H, 19.5" W, 19.5" Dp.	1.5" x 6.5"	4-100W Med. Base	
CDT1719OZ	10.5" H, 19.5" W, 19.5" Dp.	1.5" x 6.5"	4-100W Med. Base	

Rod-hung fixtures come with (2) 6" and (2) 12" Rods.

SEMI FLUSH



DAMP **QF2807VP**

Emma

FINISH: IB - Imperial Bronze
VP - Vintage Silver

GLASS: Clear Faceted



DAMP **LMT1716PN**

Limelight

FINISH: Palladian Bronze

**See matching
Dining & Foyer pg. 31*



convertible



DAMP **QF2807IB**



DAMP **TPR1716C**

Taper

FINISH: Polished Chrome

SHADE: Off White Fabric

**See matching
pendants pg. 56*



DAMP **BSN1714EK**

Basin

FINISH: Earth Black

**See matching
chandelier pg. 31*

ITEM	DIMENSIONS	CANOPIY	BULBS
BSN1714EK	15" H, 14" W, 14" Dp.	.88" x 5"	3-60W Cand. Base
LMT1716PN	13" H, 16" W, 16" Dp.	.75" x 5"	9-60W Cand. Base Vintage Bulbs Supplied
QF2807IB	14.5" H, 16.5" W, 16.5" Dp.	1.5" x 5.75"	3-60W Cand. Base
QF2807VP	14.5" H, 16.5" W, 16.5" Dp.	1.5" x 5.75"	3-60W Cand. Base
TPR1716C	11" H, 16" W, 16" Dp.	.75" x 4.75"	3-100W Med. Base



Dublin

FINISH: BN - Brushed Nickel
PN - Palladian Bronze

GLASS: Pressed Clear

DAMP **DBN8701BN**

**See matching collection pgs. 12 - 16*



DAMP **DBN8701PN**

dangling crystals →



DAMP **LVY8702WT**



DAMP **WDN8701WT**

Warden

FINISH: Western Bronze
SHADE: Light Beige Fabric

**See matching chandelier pg. 37*

Livery

FINISH: Western Bronze

**See matching collection pgs. 17 - 19*

ITEM	DIMENSIONS	BACKPLATE	HCWO	BULBS
DBN8701BN	10" H, 6.5" W, 8" Dp.	5" x 5"	5.5"	1-100W Med. Base
DBN8701PN	10" H, 6.5" W, 8" Dp.	5" x 5"	5.5"	1-100W Med. Base
LVY8702WT	18" H, 15.5" W, 9" Dp.	.75" x 5"	12.5"	2-60W Cand. Base
WDN8701WT	14" H, 7" W, 8.5" Dp.	7" x 4.5"	5.63"	1-60W Cand. Base

BATH

Westcap

FINISH: BN - Brushed Nickel
C - Polished Chrome

GLASS: Inner: Sandblasted
Outer: Clear Ripple



DAMP [WCP8602BNLED](#)



MOUNTS



DAMP [WCP8603BNLED](#)



DAMP [WCP8604BNLED](#)

ITEM	DIMENSIONS	BACKPLATE	HCW0	BULBS
WCP8602BNLED	7" H, 15" W, 5" Dp.	5" x 7.5"	4"	2-4.5W Frosted G9 LED Dimmable
WCP8603BNLED	7" H, 22.5" W, 5" Dp.	5" x 7.5"	4"	3-4.5W Frosted G9 LED Dimmable
WCP8604BNLED	7" H, 32" W, 5" Dp.	5" x 7.5"	4"	4-4.5W Frosted G9 LED Dimmable

Westcap



DAMP ■ **WCP8602CLED**



detail

MOUNTS



G9 LED Bulb

LED



DAMP ■ **WCP8604CLED**



DAMP ■ **WCP8603CLED**

ITEM	DIMENSIONS	BACKPLATE	HCW0	BULBS
WCP8602CLED	7" H, 15" W, 5" Dp.	5" x 7.5"	4"	2-4.5W Frosted G9 LED Dimmable
WCP8603CLED	7" H, 22.5" W, 5" Dp.	5" x 7.5"	4"	3-4.5W Frosted G9 LED Dimmable
WCP8604CLED	7" H, 32" W, 5" Dp.	5" x 7.5"	4"	4-4.5W Frosted G9 LED Dimmable

BATH



detail



DAMP

PSE8602CLED



G9 LED Bulb

LED



DAMP

PSE8603CLED

Passage

FINISH: Polished Chrome

GLASS: Opal Etched

MOUNTS



DAMP

PSE8604CLED

ITEM	DIMENSIONS	BACKPLATE	HCWO	BULBS
PSE8602CLED	5" H, 17" W, 5.5" Dp.	5" x 7.38"	4.87"	2-4.5W Frosted G9 LED Dimmable
PSE8603CLED	5" H, 24" W, 5.5" Dp.	5" x 7.38"	4.87"	3-4.5W Frosted G9 LED Dimmable
PSE8604CLED	5" H, 32.5" W, 5.5" Dp.	5" x 7.38"	4.87"	4-4.5W Frosted G9 LED Dimmable



detail

DAMP UNI8602PK



Bulbs Shown Not Supplied

Union

MOUNTS

FINISH: Polished Nickel

GLASS: Light Champagne

DAMP UNI8603PK



DAMP UNI8604PK



ITEM	DIMENSIONS	BACKPLATE	HCW0	BULBS
UNI8602PK	9" H, 15" W, 6.5" Dp.	5" x 5"	6.5"	2-100W Med. Base
UNI8603PK	9" H, 23" W, 6.5" Dp.	5" x 5"	6.5"	3-100W Med. Base
UNI8604PK	9" H, 31.5" W, 6.5" Dp.	5" x 5"	6.5"	4-100W Med. Base

BATH

Meridian

FINISH: Polished Chrome

GLASS: Clear Bubble



detail



G9 LED Bulb

DAMP

MRD8603CLED



MOUNTS

DAMP

MRD8604CLED



DAMP

MRD8605CLED



ITEM	DIMENSIONS	BACKPLATE	HCW0	BULBS
MRD8603CLED	5.5" H, 20" W, 7" Dp.	4.5" x 7"	3.6"	3-4.5W Frosted G9 LED Dimmable
MRD8604CLED	5.5" H, 27.5" W, 7" Dp.	4.5" x 7"	3.6"	4-4.5W Frosted G9 LED Dimmable
MRD8605CLED	5.5" H, 35.5" W, 7" Dp.	4.5" x 7"	3.6"	5-4.5W Frosted G9 LED Dimmable



DAMP

SCH8601PN

Scholar

FINISH: Palladian Bronze

GLASS: Clear Seedy



detail

Bulbs Shown Not Supplied



DAMP

SCH8602PN

MOUNTS



DAMP

SCH8603PN

ITEM	DIMENSIONS	BACKPLATE	HCW0	BULBS
SCH8601PN	9" H, 7" W, 8.5" Dp.	8" x 4.5"	4.75"	1-100W Med. Base
SCH8602PN	8" H, 18" W, 8" Dp.	4.5" x 8"	4.75"	2-100W Med. Base
SCH8603PN	8" H, 25" W, 8" Dp.	4.5" x 8"	4.75"	3-100W Med. Base

BATH

Tatum

FINISH: Polished Chrome

GLASS: Opal Etched



DAMP ■ [TU8602CLED](#)

MOUNTS



DAMP ■ [TU8603CLED](#)



DAMP ■ [TU8604CLED](#)

ITEM	DIMENSIONS	BACKPLATE	HCW0	BULBS
TU8602CLED	5" H, 13" W, 5.5" Dp.	4.5" x 7"	2.63"	2-4.5W Frosted G9 LED Dimmable
TU8603CLED	5" H, 21" W, 5.5" Dp.	4.5" x 7"	2.63"	3-4.5W Frosted G9 LED Dimmable
TU8604CLED	5" H, 29" W, 5.5" Dp.	4.5" x 10"	2.63"	4-4.5W Frosted G9 LED Dimmable

DAMP

HLD8602PK



Holland

FINISH: Polished Nickel

GLASS: Opal Etched

MOUNTS

DAMP

HLD8603PK



DAMP

HLD8604PK



ITEM

DIMENSIONS

BACKPLATE

HCW0

BULBS

HLD8602PK

6.5" H, 14" W, 5.5" Dp.

4.5" x 7"

4.5"

2-100W Med. Base

HLD8603PK

6.5" H, 22" W, 7.5" Dp.

4.5" x 7"

4.5"

3-100W Med. Base

HLD8604PK

6.5" H, 28" W, 7.5" Dp.

4.5" x 7"

4.5"

4-100W Med. Base

OUTDOOR



by QUOIZEL

5-Year Finish Warranty



front view



Crusade

FINISH: EK - Earth Black

GLASS: Clear Seedy

Bulbs Shown Not Supplied

WET

CSE8410EK

Bulbs Shown Not Supplied



Indoor
Outdoor

WET

CSE1910EK



WET

CSE8406EK



WET

CSE8408EK

Crusade



WET

CSE9010EK

ITEM	DIMENSIONS	BACKPLATE/CANOPY	HCWO	BULBS
CSE1910EK	15.5" H, 10" W, 10" Dp.	1" x 5"		1-150W Med. Base
CSE8406EK	11" H, 6" W, 8" Dp.	6.5" x 4"	3.75"	1-100W Med. Base
CSE8408EK	14.5" H, 8" W, 10" Dp.	7" x 4.75"	4.75"	1-100W Med. Base
CSE8410EK	18" H, 10" W, 12" Dp.	8" x 5.25"	5.75"	1-150W Med. Base
CSE9010EK	17.5" H, 10" W, 10" Dp.			1-150W Med. Base

Outdoor fixtures come with 12' of wire and 8' of chain.

OUTDOOR



front view



Crusade

FINISH: EK - Earth Black

GLASS: Clear Seedy



Bulbs Shown Not Supplied

WET

CSE8410PN

Crusade

Indoor
Outdoor

WET CSE1910PN

WET CSE8406PN

Bulbs Shown Not Supplied



WET CSE9010PN



WET CSE8408PN

ITEM	DIMENSIONS	BACKPLATE/CANOPY	HCWO	BULBS
CSE1910PN	15.5" H, 10" W, 10" Dp.	1" x 5"		1-150W Med. Base
CSE8406PN	11" H, 6" W, 8" Dp.	6.5" x 4"	3.75"	1-100W Med. Base
CSE8408PN	14.5" H, 8" W, 10" Dp.	7" x 4.75"	4.75"	1-100W Med. Base
CSE8410PN	18" H, 10" W, 12" Dp.	8" x 5.25"	5.75"	1-150W Med. Base
CSE9010PN	17.5" H, 10" W, 10" Dp.			1-150W Med. Base

Outdoor fixtures come with 12' of wire and 8' of chain.

OUTDOOR

Newbury

FINISH: Mystic Black

GLASS: Clear Beveled



front view



INTEGRATED **LED**
10 YEAR WARRANTY

LED CHART

Lumens	1,300
Total Watts	16W
Color Rendering Index (CRI)	80
Color Temperature (CCT)	2,700K
Dimmable	NO

WET

NYCL8411K

INTEGRATED **LED**
10 YEAR WARRANTY

NYCL8407K

LED CHART

Lumens	800
Total Watts	11W
Color Rendering Index (CRI)	80
Color Temperature (CCT)	2,700K
Dimmable	NO



WET NYCL8407K

Indoor
Outdoor

WET NYCL1911K



Newbury



WET NYCL9011K



WET NYCL8409K

ITEM	DIMENSIONS	BACKPLATE/CANOPY	HCWO	LIGHT SOURCE
NYCL1911K	19" H, 11" W, 11" Dp.	1" x 5"		See Chart for LED Information
NYCL8407K	12.5" H, 7" W, 7" Dp.	5" x 4.75"	6"	See Chart for LED Information
NYCL8409K	14" H, 8.5" W, 8" Dp.	5" x 4.75"	7"	See Chart for LED Information
NYCL8411K	20" H, 11" W, 10" Dp.	9" x 4.75"	9"	See Chart for LED Information
NYCL9011K	21.5" H, 11" W, 10" Dp.			See Chart for LED Information

Outdoor fixtures come with 12' of wire and 8' of chain.

OUTDOOR

Newbury

FINISH: Medici Bronze

GLASS: Clear Beveled



front view



INTEGRATED **LED**
10 YEAR WARRANTY

LED CHART

Lumens	1,300
Total Watts	16W
Color Rendering Index (CRI)	80
Color Temperature (CCT)	2,700K
Dimmable	NO

WET

NYCL8411Z

Indoor
Outdoor

INTEGRATED LED
10 YEAR WARRANTY



WET NYCL1911Z



WET NYCL8407Z

NYCL8407Z

LED CHART

Lumens	800
Total Watts	11W
Color Rendering Index (CRI)	80
Color Temperature (CCT)	2,700K
Dimmable	NO



Newbury

WET NYCL9011Z

WET NYCL8409Z



ITEM	DIMENSIONS	BACKPLATE/CANOPY	HCW0	LIGHT SOURCE
NYCL1911Z	19" H, 11" W, 11" Dp.	1" x 5"		See Chart for LED Information
NYCL8407Z	12.5" H, 7" W, 7" Dp.	5" x 4.75"	6"	See Chart for LED Information
NYCL8409Z	14" H, 8.5" W, 8" Dp.	5" x 4.75"	7"	See Chart for LED Information
NYCL8411Z	20" H, 11" W, 10" Dp.	9" x 4.75"	9"	See Chart for LED Information
NYCL9011Z	21.5" H, 11" W, 10" Dp.			See Chart for LED Information

Outdoor fixtures come with 12' of wire and 8' of chain.



front view



Lighthouse

FINISH: Palladian Bronze

GLASS: Clear Seedy

Bulbs Shown Not Supplied

WET

LTE8409PN

Indoor
Outdoor

Bulbs Shown Not Supplied

WET LTE1909PN



WET LTE8406PN



Lighthouse

WET LTE8407PN



WET LTE9009PN



ITEM	DIMENSIONS	BACKPLATE/CANOPY	HCWO	BULBS
LTE1909PN	19" H, 8.5" W, 8.5" Dp.	1" x 5"		1-150W Med. Base
LTE8406PN	13.5" H, 5.5" W, 6.5" Dp.	6.5" x 4.5"	4.75"	1-100W Med. Base
LTE8407PN	17" H, 7" W, 8.5" Dp.	6.5" x 4.5"	5.5"	1-100W Med. Base
LTE8409PN	20" H, 8.5" W, 9.5" Dp.	8" x 4.75"	6.5"	1-150W Med. Base
LTE9009PN	22" H, 8.5" W, 8.5" Dp.		6.5"	1-150W Med. Base



front view



Carriage

FINISH: Mottled Black

GLASS: Clear Seedy

Bulbs Shown Not Supplied

WET

CRG8410MB

Carriage

WET CRG8406MB



Indoor
Outdoor

WET CRG1910MB



Bulbs Shown Not Supplied

WET CRG9010MB



WET CRG8408MB



ITEM	DIMENSIONS	BACKPLATE/CANOPY	HCWO	BULBS
CRG1910MB	21.5" H, 10" W, 10" Dp.	.88" x 4.38"		1-150W Med. Base
CRG8406MB	11.5" H, 6" W, 7" Dp.	6.5" x 4.5"	4"	1-100W Med. Base
CRG8408MB	15" H, 8" W, 9" Dp.	7" x 4.5"	4.5"	1-100W Med. Base
CRG8410MB	19" H, 10" W, 11.5" Dp.	9" x 5"	5.5"	1-150W Med. Base
CRG9010MB	21.75" H, 10" W, 10" Dp.			1-150W Med. Base

front view



Boardwalk

FINISH: Mottled Black

GLASS: Clear Seedy

Bulbs Shown Not Supplied

WET

BRD8410MB



Indoor
Outdoor

Bulbs Shown Not Supplied

WET BRD1910MB



WET BRD8406MB



Boardwalk

WET BRD9010MB



WET BRD8408MB

ITEM	DIMENSIONS	BACKPLATE/CANOPY	HCW	BULBS
BRD1910MB	18.5" H, 10" W, 10" Dp.	1" x 5"		1-150W Med. Base
BRD8406MB	10" H, 6" W, 7.5" Dp.	5" x 5"	2.5"	1-100W Med. Base
BRD8408MB	14" H, 8" W, 9.5" Dp.	6" x 6"	3"	1-100W Med. Base
BRD8410MB	17.5" H, 10" W, 11.5" Dp.	6.5" x 6.5"	3.5"	1-150W Med. Base
BRD9010MB	19.5" H, 10" W, 10" Dp.			1-150W Med. Base

Outdoor fixtures come with 12' of wire and 8' of chain.

OUTDOOR

front view



Everglade

FINISH: Earth Black

GLASS: Clear Water

WET

EVG8411EK

WET EVG8407EK



Indoor
Outdoor

WET EVG1911EK



Everglade

WET EVG9011EK



WET EVG8409EK



ITEM	DIMENSIONS	BACKPLATE/CANOPY	HCW0	BULBS
EVG1911EK	19" H, 10.5" W, 10.5" Dp.	.88" x 4.38"		1-150W Med. Base
EVG8407EK	12.5" H, 6.5" W, 7.5" Dp.	6.5" x 4.5"	2.5"	1-100W Med. Base
EVG8409EK	15" H, 8.5" W, 9.5" Dp.	7" x 4.5"	2.5"	1-100W Med. Base
EVG8411EK	18" H, 10.5" W, 11.5" Dp.	9" x 5"	3"	1-150W Med. Base
EVG9011EK	20.5" H, 10.5" W, 10.5" Dp.			1-150W Med. Base

Outdoor fixtures come with 12' of wire and 8' of chain.

OUTDOOR

front view



Ravine

FINISH: Western Bronze

GLASS: Clear Beveled

Bulbs Shown Not Supplied

WET

RAV8410WT

Indoor
Outdoor

Bulbs Shown Not Supplied

WET RAV1910WT



WET RAV8406WT



Ravine

WET RAV8408WT



WET RAV9010WT



ITEM	DIMENSIONS	BACKPLATE/CANOPY	HCWO	BULBS
RAV1910WT	20" H, 10" W, 10" Dp.	1" x 5"		1-150W Med. Base
RAV8406WT	12.5" H, 6" W, 7.5" Dp.	6" x 4.5"	4.75"	1-100W Med. Base
RAV8408WT	16.5" H, 8" W, 9.5" Dp.	8" x 4.5"	5.75"	1-100W Med. Base
RAV8410WT	20" H, 10" W, 11.5" Dp.	10" x 5.5"	7"	1-150W Med. Base
RAV9010WT	22.5" H, 10" W, 10" Dp.			1-150W Med. Base

Outdoor fixtures come with 12' of wire and 8' of chain.

front view



Terrace

FINISH: Mystic Black

GLASS: Outer - Seedy
Inner - Opal Etched



TRE8409K

WET TRE8406K



Indoor
Outdoor

WET TRE1909K



Terrace

WET TRE9009K



WET TRE8407K



ITEM	DIMENSIONS	BACKPLATE/CANOPY	HCWO	BULBS
TRE1909K	17" H, 8.5" W, 7.5" Dp.	1" x 5"		1-150W Med. Base
TRE8406K	12.5" H, 5.5" W, 7" Dp.	6" x 4.5"	5"	1-100W Med. Base
TRE8407K	14" H, 7" W, 8.5" Dp.	7" x 4.5"	5.5"	1-100W Med. Base
TRE8409K	17" H, 8.5" W, 10" Dp.	8.25" x 4.5"	6.75"	1-150W Med. Base
TRE9009K	18" H, 8.5" W, 7.5" Dp.			1-150W Med. Base

Outdoor fixtures come with 12' of wire and 8' of chain.

OUTDOOR



front view



Goldenrod

FINISH: Western Bronze
with Brass Rod Accents

GLASS: Clear

Bulbs Shown Not Supplied

WET

GLD8410WT

Indoor
Outdoor

WET GLD1910WT

Bulbs Shown Not Supplied



WET GLD8406WT



Goldenrod

WET GLD8408WT



WET GLD9010WT



ITEM	DIMENSIONS	BACKPLATE/CANOPY	HCWO	BULBS
GLD1910WT	20" H, 10" W, 10" Dp.	1" x 5"		1-150W Med. Base
GLD8406WT	13" H, 6" W, 7" Dp.	5.75" x 4.5"	4.5"	1-100W Med. Base
GLD8408WT	16.5" H, 8.5" W, 9" Dp.	8" x 4.5"	6"	1-100W Med. Base
GLD8410WT	20" H, 10" W, 11" Dp.	9.75" x 4.5"	7.5"	1-150W Med. Base
GLD9010WT	22" H, 10" W, 10" Dp.			1-150W Med. Base

Outdoor fixtures come with 12' of wire and 8' of chain.

OUTDOOR



front view



INTEGRATED LED
10 YEAR WARRANTY

LED CHART

Lumens	715
Total Watts	11W
Color Rendering Index (CRI)	80
Color Temperature (CCT)	2,700K
Dimmable	NO

Beachside

FINISH: Galvanized



INTEGRATED LED
10 YEAR WARRANTY

LED CHART

Lumens	980
Total Watts	14W
Color Rendering Index (CRI)	80
Color Temperature (CCT)	2,700K
Dimmable	NO

ITEM	DIMENSIONS	BACKPLATE	HCWO	BULBS
BCE8410GV	10" H, 10" W, 15" Dp.	5" x 5"	5"	See Chart for LED Information
BCE8414GV	14.5" H, 14" W, 21" Dp.	7" x 7"	7"	See Chart for LED Information

TIFFANY



GU24 Socket and CFL Bulbs Not Shown.



Inglenook

FINISH: Valiant Bronze

Indoor
Outdoor



ITEM	DIMENSIONS	BACKPLATE	HCWO	BULBS	GLASS
TFIK1611VA	6" H, 11" W, 11" Dp.			2-60W Med. Base	Contains 220 Pieces of Tiffany Glass
TFIK8407VA	10.5" H, 7" W, 9" Dp.	6.5" x 4.5"	6.5"	1-100W Med. Base	Contains 38 Pieces of Tiffany Glass
TFIK8409VA	12" H, 8.5" W, 10.5" Dp.	7.5" x 4.5"	6.75"	1-100W Med. Base	Contains 38 Pieces of Tiffany Glass
TFIK8411VA	14" H, 11" W, 13" Dp.	8.5" x 4.5"	7.75"	1-150W Med. Base	Contains 38 Pieces of Tiffany Glass

TIFFANY

Violets

FINISH: Vintage Bronze



TFVT9362VB



TFVT1820VB



TFVT6323VB



DAMP **TFVT1617VB**

ITEM	DIMENSIONS	CANOPY	BULBS	GLASS
TFVT1617VB	5.5" H, 16.5" W, 16.5" Dp.	1" x 7"	2-75W Med. Base	Contains 361 Pieces of Tiffany Glass
TFVT1820VB	10.5" H, 20" W, 20" Dp.	2" x 5.5"	3-100W Med. Base	Contains 465 Pieces of Tiffany Glass
TFVT6323VB	23.5" H, 16" W, 16" Dp.		2-75W Med. Base	Contains 416 Pieces of Tiffany Glass
TFVT9362VB	62" H, 18" W, 18" Dp.		2-100W Med. Base	Contains 416 Pieces of Tiffany Glass



TFGD9361VB



TFGD1617VB



TFGD6324VB

Garland

FINISH: Vintage Bronze



TFGD1820VB

ITEM	DIMENSIONS	CANOPY	BULBS	GLASS
TFGD1617VB	6" H, 16.5" W, 16.5" Dp.	1" x 7"	2-75W Med. Base	Contains 240 Pieces of Tiffany Glass
TFGD1820VB	10.5" H, 19.5" W, 19.5" Dp.	2" x 5.5"	3-100W Med. Base	Contains 250 Pieces of Tiffany Glass
TFGD6324VB	23.5" H, 16" W, 16" Dp.		2-75W Med. Base	Contains 240 Pieces of Tiffany Glass
TFGD9361VB	61.5" H, 18" W, 18" Dp.		2-100W Med. Base	Contains 240 Pieces of Tiffany Glass

Fixtures come with 8' of wire and 4' of chain.

TIFFANY

Alcott

FINISH: Valiant Bronze



DAMP

TFAT1617VA



TF2802TIB

Blossom

FINISH: Imperial Bronze

TF2802FIB



Legend

FINISH: Western Bronze

TF2804TWT



Sunrays

FINISH: Western Bronze

TF2806TWT



ITEM	DIMENSIONS	CANOPY	BULBS	GLASS
TFAT1617VA	5.5" H, 16.5" W, 16.5" Dp.	1" x 7"	2-75W Med. Base	Contains 312 Pieces of Tiffany Glass
TF2802FIB	58.5" H, 18" W, 18" Dp.		2-100W Med. Base	Contains 332 Pieces of Tiffany Glass
TF2802TIB	27" H, 18" W, 18" Dp.		2-75W Med. Base	Contains 332 Pieces of Tiffany Glass
TF2804TWT	24.5" H, 17.5" W, 17.5" Dp.		2-75W Med. Base	Contains 32 Pieces of Tiffany Glass
TF2806TWT	25" H, 18" W, 18" Dp.		2-75W Med. Base	Contains 102 Pieces of Tiffany Glass

TF2801TVB



Hummingbird

FINISH: Vintage Bronze

TF2801FVB



Meadow

FINISH: Russet



TF2805TRS

Blue Trellis

FINISH: Russet



TF2803TRS

ITEM

DIMENSIONS

BULBS

GLASS

TF2801FVB	62" H, 18" W, 18" Dp.	2-100W Med. Base	Contains 540 Pieces of Tiffany Glass
TF2801TVB	23" H, 16" W, 16" Dp.	2-75W Med. Base	Contains 498 Pieces of Tiffany Glass
TF2803TRS	24" H, 18.5" W, 18.5" Dp.	2-75W Med. Base	Contains 726 Pieces of Tiffany Glass
TF2805TRS	23.5" H, 16.5" W, 16.5" Dp.	2-75W Med. Base	Contains 360 Pieces of Tiffany Glass

TABLE & FLOOR



VVBY9362BN



VVBY9362OI

Broadway

FINISH: BN - Brushed Nickel
OI - Oil Rubbed Bronze

SHADE: BN - White Fabric
OI - Beige Fabric



ITEM

VVBY9362BN

DIMENSIONS

61.5" H, 17" W, 17" Dp.

BULBS

3-75W Med. Base

SHADE DIMS

(9" x 17") x (17" x 17") x 17"

VVBY9362OI

61.5" H, 17" W, 17" Dp.

3-75W Med. Base

(9" x 17") x (17" x 17") x 17"

MIRRORS

Shoreline

FINISH: Black Textured

QR2793



Grace

FINISH: Black

QR2800



QR2792

Vanderbilt

FINISH: CS - Century Silver Leaf
PN - Palladian Bronze

QR2791

ITEM

QR2791

QR2792

QR2793

QR2800

DIMENSIONS

48" H, 32" W, 2" Dp.

48" H, 32" W, 2" Dp.

26" H, 26" W, 3" Dp.

33" H, 24" W, 1" Dp.

GLASS

Beveled

Beveled

Beveled

Beveled

MIRRORS

Monarch

FINISH: Gold



QR2799



QR2795

Artiste

FINISH: Black



QR2798

ITEM

QR2795

DIMENSIONS

30" H, 20" W, .5" Dp.

GLASS

Beveled

QR2798

40" H, 30.5" W, .5" Dp.

Beveled

QR2799

36" H, 24" W, .5" Dp.

Beveled

Artiste

FINISH: Silver

QR2797



Artiste

FINISH: Black

QR2794



Artiste

FINISH: Gold

QR2796



ITEM

QR2794

DIMENSIONS

50" H, 20" W, .5" Dp.

GLASS

Beveled

QR2796

30" H, 20" W, .5" Dp.

Beveled

QR2797

30" H, 20" W, .5" Dp.

Beveled



INDEX

collection

ANA5005K.....	32	CSE8406PN.....	77	HE1505BN	60
ANA5008K.....	33	CSE8408EK	75	HE5003BN	30
ANA5009K.....	33	CSE8408PN.....	77	HE5005BN	30
ANA5015K.....	32	CSE8410EK	74	HE5009BN	30
AVY5203PK.....	23	CSE8410PN.....	76	HLD8602PK.....	73
AVY5203PN	22	CSE9010EK	75	HLD8603PK.....	73
AVY5204PK.....	23	CSE9010PN.....	77	HLD8604PK.....	73
AVY5204PN	22	CTS2822PK	53	JBE2822K.....	34
AVY5206PK.....	23	CTS2822WT.....	53	JBE5204K.....	34
AVY5206PN	22	DBN1506K	13	JBE5208K.....	34
AVY654PK.....	24, 51	DBN5005BN.....	15	LGE5005GK	36
AVY654PN	24, 51	DBN5005K	13	LMT1716PN	64
BCE8410GV	96	DBN5009BN.....	14	LMT5009PN	31
BCE8414GV	96	DBN5009K	12	LMT5012PN	31
BGE2822AP.....	53	DBN5103BN.....	15	LTE1909PN.....	83
BGE2822WT	53	DBN5103K	13	LTE8406PN.....	83
BRD1910MB.....	87	DBN8602PN.....	16	LTE8407PN.....	83
BRD8406MB.....	87	DBN8603PN.....	16	LTE8409PN.....	82
BRD8408MB.....	87	DBN8604PN.....	16	LTE9009PN.....	83
BRD8410MB.....	86	DBN8701BN.....	15, 65	LVY1716WT.....	19
BRD9010MB.....	87	DBN8701PN.....	16, 65	LVY2821WT.....	19
BSN1714EK.....	64	DWL5204WT	36	LVY5004WT	19
BSN5006EK.....	31	DWL540WT	52	LVY5005WT.....	18
CCT2814WT	57	EON1715WT	27	LVY5009WT.....	17
CCT2824WT	57	EON2823WT	27	LVY8702WT.....	18, 65
CCT2830WT	57	EON5006WT	27	LXY1506IB	59
CDT1715BN	63	EON5009WT	26	LXY1506VG.....	59
CDT1715OZ	63	EVG1911EK	89	LXY2817IB	54
CDT1719BN	63	EVG8407EK	89	LXY2817VG.....	54
CDT1719OZ	63	EVG8409EK	89	LXY2822IB	54
CNT5005VG	37	EVG8411EK	88	LXY2822VG.....	54
CNT5204VG	37	EVG9011EK	89	MRD8603CLED	70
CRG1910MB.....	85	GLA2816VZ.....	55	MRD8604CLED	70
CRG8406MB.....	85	GLA2824VZ.....	55	MRD8605CLED	70
CRG8408MB.....	85	GLD1910WT.....	95	NYCL1911K.....	79
CRG8410MB.....	84	GLD8406WT.....	95	NYCL1911Z.....	81
CRG9010MB.....	85	GLD8408WT.....	95	NYCL8407K.....	79
CRV536WT	52	GLD8410WT.....	94	NYCL8407Z.....	81
CRY1716PN.....	25	GLD9010WT.....	95	NYCL8409K.....	79
CRY5005PN.....	25	GLY5203BA	29	NYCL8409Z.....	81
CRY5006PN.....	25	GLY5204BA	29	NYCL8411K.....	78
CRY5009PN.....	25	GLY5206BA	29	NYCL8411Z.....	80
CSE1910EK	75	GLY648BA	28, 51	NYCL9011K.....	79
CSE1910PN.....	77	GZ5204GK	35	NYCL9011Z.....	81
CSE8406EK	75	HE1505BN	30, 60	ON1509BN.....	59

INDEX

ON1509WT	59	QF2782DC	56	TF2802TIB	100
PCAB1614C.....	46	QF2783C	57	TF2803TRS	101
PCBB8520C.....	48	QF2787VG	58	TF2804TWT.....	100
PCBB8526C.....	48	QF2807IB	64	TF2805TRS	101
PCBB8532C.....	48	QF2807VP.....	64	TF2806TWT.....	100
PCBC8518C.....	50	QPP2781BN	60	TFAT1617VA.....	100
PCBC8526C.....	50	QPP2784C.....	61	TFGD1617VB	99
PCBL1614BN.....	42	QPP2785C.....	61	TFGD1820VB	99
PCBL2817BN.....	42	QPP2788K.....	62	TFGD6324VB	99
PCBL2821BN.....	42	QPP2789K.....	62	TFGD9361VB	99
PCBZ1712C	46	QPP2790K.....	61	TFIK1611VA	97
PCBZ1716C	46	QPP2816BN	61	TFIK8407VA	97
PCCD1613C	44	QPP2817K.....	62	TFIK8409VA	97
PCCD1615C	44	QPP2818K.....	60	TFIK8411VA	97
PCEB8518C.....	49	QR2791	103	TFVT1617VB	98
PCEB8524C	49	QR2792	103	TFVT1820VB	98
PCEB8530C.....	49	QR2793	103	TFVT6323VB	98
PCEM1619C	47	QR2794	105	TFVT9362VB	98
PCFL8522C.....	47	QR2795	104	TPR1716C.....	64
PCFL8531C.....	47	QR2796	105	TPR2816C.....	56
PCGD8522C	50	QR2797	105	TPR2823C.....	56
PCGD8531C	50	QR2798	104	TRE1909K	93
PCIN1504C.....	39	QR2799	104	TRE8406K	93
PCIN1716C.....	38	QR2800	103	TRE8407K	93
PCIN1828C.....	38	RAV1910WT	91	TRE8409K	92
PCIN540C.....	39	RAV8406WT	91	TRE9009K	93
PCIN8518C.....	40	RAV8408WT	91	TTA2817K.....	55
PCIN8527C.....	40	RAV8410WT	90	TTA2824K.....	55
PCIN8536C.....	40	RAV9010WT	91	TU8602CLED	72
PCIT1612C	42	SCH8601PN	71	TU8603CLED	72
PCIT1616C	42	SCH8602PN	71	TU8604CLED	72
PCMC2816C.....	45	SCH8603PN	71	UNI8602PK	69
PCMC2820C.....	45	SDM2814K.....	58	UNI8603PK	69
PCMT1614C	41	SDM2824K.....	58	UNI8604PK	69
PCMT1614W	41	SQR1504RK	20	VRA5204WT.....	36
PCPG2816C.....	43	SQR5005RK	20	VVBY9362BN	102
PCPG2824C.....	43	SQR538RK	21, 52	VVBY9362OI	102
PCPN2816PK	41	SQR8602RK	21	WCP8602BNLED.....	66
PCPN832PK	41	SQR8603RK	21	WCP8602CLED	67
PCTE1610C	44	SQR8701RK	21	WCP8603BNLED.....	66
PCTE1616C	44	SRN5204MK.....	35	WCP8603CLED	67
PSE8602CLED	68	SRN5208MK.....	35	WCP8604BNLED.....	66
PSE8603CLED	68	TF2801FVB.....	101	WCP8604CLED	67
PSE8604CLED	68	TF2801TVB.....	101	WDN5004WT	37
QF2773K.....	56	TF2802FIB.....	100	WDN8701WT	65



BELGRADE

collection

www.QUOIZEL.com

Corporate Headquarters

6 Corporate Parkway, Goose Creek, SC 29445
Phone: (843) 553-6700

Corporate Headquarters/ Customer Service

590 Old Willets Path, Hauppauge, NY 11788
Phone: (631) 273-2700
Fax: (631) 231-7102
Toll-Free Consumer Hotline: (800) 645-3184

Showroom - Dallas Trade Mart

3rd Floor, Space 3200, Dallas, TX 75207
Phone: (214) 747-3665



CQ2117X

© Quozel, Inc.

QUOIZEL.
Artisans in Lighting...since 1930

