

NOTEWORTHY  
2016-2017



NOTEWORTHY  
2016-2017

 **SATCO**<sup>®</sup> | **NUVO**<sup>®</sup>  
LIGHTING

NUVO



# 2016-2017

Design, technology and the experience of quality lighting.

As lighting continues to evolve, it's easy to get caught up in exciting new technologies, but lose sight of good design. At Nuvo Lighting, we're well aware of all the new LED advances, and employ many of them in our latest fixtures. But not just because they are new. We use them when they can unlock new design possibilities, and in the end, deliver a higher quality lighting experience. Any venue, large or small, indoors or out, will benefit from lighting that's beautifully designed and technologically advanced.

Get to know Nuvo. There's so much to design!

## Contents

Timone .....	4	Vessel LED .....	68
Meadow .....	8	Del LED .....	70
Filigree .....	12	Pulse LED .....	72
Seneca .....	14	Hawk LED .....	74
Krys .....	18	Decor LED .....	76
Sherwood .....	26	Grill LED .....	78
Boxer .....	30	Pace LED .....	80
Kettle .....	32	Loop LED .....	82
Lake .....	34	Slice LED .....	84
Bandit .....	38	Bungalow LED .....	86
Iron .....	42	Essex LED .....	88
Fern .....	44	Winthrop LED .....	90
Maxx .....	46	Roxton LED .....	92
Crate LED .....	50	Howell .....	94
Tess LED .....	52	LED Track Heads .....	96
Thorn LED .....	60	Twist and Lock LED .....	98
Doral LED .....	62	Puff LED .....	100
Thrust LED .....	64	Mushroom LED .....	104
Tex LED .....	66	INDEX .....	106



On the cover:  
Nuvo Lighting's Sherwood 8 light Chandelier  
in Iron Black with Brushed Nickel Accents  
and Clear Glass, (page 26).

On the opposite page:  
Nuvo Lighting's Timone 8 Light Chandelier  
in Vintage Brass with Etched Sandstone Glass,  
(page 6).

contents

# TIMONE



## 8 Light Chandelier

**60-5092** Polished Nickel / Etched Sandstone Glass

(8) 100W A19 max. / Medium Base

Dimensions: Width 27<sup>3</sup>/<sub>8</sub>", Height 20<sup>1</sup>/<sub>8</sub>",  
Chain 48", Wire 12'

Accessories:

**25-5092** 3' Section of matching chain



### 4 Light Chandelier

**60-5091** Polished Nickel / Etched Sandstone Glass

(4) 100W A19 max. / Medium Base

Dimensions: Width 23", Height 9 $\frac{1}{8}$ ",  
Chain 48", Wire 12'

Accessories:

**25-5092** 3' Section of matching chain



### 6 Light Pendant

**60-5094** Polished Nickel / Etched Sandstone Glass

(6) 100W A19 max. / Medium Base

Dimensions: Width 18 $\frac{3}{4}$ ", Height 30 $\frac{3}{8}$ ",  
Chain 48", Wire 12'

Accessories:

**25-5092** 3' Section of matching chain



### 4 Light Trestle

**60-5093** Polished Nickel / Etched Sandstone Glass

(4) 100W A19 max. / Medium Base

Dimensions: Length 36", Width 8 $\frac{1}{4}$ ", Height 19",  
Chain 48", Wire 12'

Accessories:

**25-5092** 3' Section of matching chain

timone

# TIMONE



## 8 Light Chandelier

**60-5082** Vintage Brass / Etched Sandstone Glass

(8) 100W A19 max. / Medium Base

Dimensions: Width 27<sup>3</sup>/<sub>8</sub>", Height 20<sup>1</sup>/<sub>8</sub>",  
Chain 48", Wire 12'

Accessories:

**25-5082** 3' Section of matching chain



### 4 Light Chandelier

**60-5081** Vintage Brass / Etched Sandstone Glass  
(4) 100W A19 max. / Medium Base  
Dimensions: Width 23", Height 9 1/8",  
Chain 48", Wire 12'  
Accessories:  
**25-5082** 3' Section of matching chain



### 6 Light Pendant

**60-5084** Vintage Brass / Etched Sandstone Glass  
(6) 100W A19 max. / Medium Base  
Dimensions: Width 18 3/4", Height 30 3/8",  
Chain 48", Wire 12'  
Accessories:  
**25-5082** 3' Section of matching chain



### 4 Light Trestle

**60-5083** Vintage Brass / Etched Sandstone Glass  
(4) 100W A19 max. / Medium Base  
Dimensions: Length 36", Width 8 1/4", Height 19",  
Chain 48", Wire 12'  
Accessories:  
**25-5082** 3' Section of matching chain



# MEADOW



## 4 Light Pendant

**60-5881** Polished Nickel / White Fabric Shade /  
Frosted Glass Diffuser

(4) 60W A19 max. / Medium Base

Dimensions: Width 24", Height 21 3/4",  
Overall Height 58" Adjustable, Wire 12'

Accessories:

Additional Stem Lengths

**25-4118** (6"), **25-4119** (12")





### 3 Light Semi-Flush

**60-5883** Polished Nickel / White Fabric Shade / Frosted Glass Diffuser

(3) 60W A19 max. / Medium Base

Dimensions: Width 16", Height 11<sup>7</sup>/<sub>8</sub>", Wire 12'

Accessories:

**25-4143** Pendant conversion kit

**25-4141** 3' Section of matching chain



### Mini Pendant

**60-5884** Polished Nickel / White Fabric Shade

(1) 60W A19 max. / Medium Base

Dimensions: Width 6<sup>1</sup>/<sub>2</sub>", Height 12<sup>5</sup>/<sub>8</sub>", Overall Height 51<sup>1</sup>/<sub>8</sub>" Adjustable, Wire 12'

Accessories:

Additional Stem Lengths

**25-4118** (6"), **25-4119** (12")



### 4 Light Foyer

**60-5885** Polished Nickel / White Fabric Shade / Frosted Glass Diffuser

(4) 60W A19 max. / Medium Base

Dimensions: Width 17", Height 32", Overall Height 68" Adjustable, Wire 12'

Accessories:

Additional Stem Lengths

**25-4118** (6"), **25-4119** (12")



### 3 Light Foyer

**60-5882** Polished Nickel / White Fabric Shade / Frosted Glass Diffuser

(3) 60W A19 max. / Medium Base

Dimensions: Width 14", Height 24<sup>1</sup>/<sub>2</sub>", Overall Height 60" Adjustable, Wire 12'

Accessories:

Additional Stem Lengths

**25-4118** (6"), **25-4119** (12")



# MEADOW



## 4 Light Pendant

**60-5886** Russet Bronze / White Fabric Shade /  
Frosted Glass Diffuser

(4) 60W A19 max. / Medium Base

Dimensions: Width 24", Height 21 3/4",  
Overall Height 58" Adjustable, Wire 12'

Accessories:

Additional Stem Lengths

**25-5886** (6"), **25-5887** (12")



### 3 Light Semi-Flush

**60-5888** Russet Bronze / White Fabric Shade / Frosted Glass Diffuser

(3) 60W A19 max. / Medium Base

Dimensions: Width 16", Height 11<sup>7</sup>/<sub>8</sub>", Wire 12'

Accessories:

**25-5888** Pendant conversion kit

**25-5112** 3' Section of matching chain



### Mini Pendant

**60-5889** Russet Bronze / White Fabric Shade

(1) 60W A19 max. / Medium Base

Dimensions: Width 6<sup>1</sup>/<sub>2</sub>", Height 12<sup>5</sup>/<sub>8</sub>", Overall Height 51<sup>1</sup>/<sub>8</sub>" Adjustable, Wire 12'

Accessories:

Additional Stem Lengths

**25-5886** (6"), **25-5887** (12")



### 4 Light Foyer

**60-5890** Russet Bronze / White Fabric Shade / Frosted Glass Diffuser

(4) 60W A19 max. / Medium Base

Dimensions: Width 17", Height 32", Overall Height 68" Adjustable, Wire 12'

Accessories:

Additional Stem Lengths

**225-5886** (6"), **25-5887** (12")



### 3 Light Foyer

**60-5887** Russet Bronze / White Fabric Shade / Frosted Glass Diffuser

(3) 60W A19 max. / Medium Base

Dimensions: Width 14", Height 24<sup>1</sup>/<sub>2</sub>", Overall Height 60" Adjustable, Wire 12'

Accessories:

Additional Stem Lengths

**225-5886** (6"), **25-5887** (12")



# FILIGREE



## 3 Light Pendant

**60-5964** Natural Brass / Beige Linen Fabric Shade / Frosted Glass Diffuser

(3) 60W A19 max. / Medium Base

Dimensions: Width 17½", Height 7⅝", Overall Height 45⅛" Adjustable, Wire 12'

Accessories:

Additional Stem Lengths

**25-4151** (6"), **25-4152** (12")



## 2 Light Flush

**60-5961** Natural Brass / Beige Linen Fabric Shade / Frosted Glass Diffuser

(2) 60W A19 max. / Medium Base

Dimensions: Width 15", Height 8"



## 2 Light Semi-Flush

**60-5967** Natural Brass / Beige Linen Fabric Shade / Frosted Glass Diffuser

(2) 60W A19 max. / Medium Base

Dimensions: Width 15", Height 12½", Wire 12'

Accessories:

**25-4161** Pendant conversion kit

**25-4153** 3' Section of matching chain



### 2 Light Flush

**60-5942** Brushed Nickel / White Linen Fabric Shade / Frosted Glass Diffuser

(2) 60W A19 max. / Medium Base

Dimensions: Width 14<sup>5</sup>/<sub>8</sub>", Height 8"



### 2 Light Flush

**60-5931** Natural Brass / Beige Linen Fabric Shade / Frosted Glass Diffuser

(2) 60W A19 max. / Medium Base

Dimensions: Width 15", Height 8"



### 2 Light Semi-Flush

**60-5948** Brushed Nickel / White Linen Fabric Shade / Frosted Glass Diffuser

(2) 60W A19 max. / Medium Base

Dimensions: Width 14<sup>5</sup>/<sub>8</sub>", Height 12<sup>1</sup>/<sub>2</sub>", Wire 12'

Accessories:

**25-1403** Pendant conversion kit

**25-1069** 3' Section of matching chain



### 2 Light Semi-Flush

**60-5937** Natural Brass / Beige Linen Fabric Shade / Frosted Glass Diffuser

(2) 60W A19 max. / Medium Base

Dimensions: Width 15", Height 12<sup>1</sup>/<sub>2</sub>", Wire 12'

Accessories:

**25-4161** Pendant conversion kit

**25-4153** 3' Section of matching chain



# SENECA



## 4 Light Large Pendant

**60-5896** Mahogany Bronze with wrapped rope /  
Beige Linen Fabric Shade / Etched Glass Diffuser

(4) 60W A19 max. / Medium Base

Dimensions: Width 22", Height 22<sup>1</sup>/<sub>8</sub>",  
Overall Height 60<sup>1</sup>/<sub>8</sub>" Adjustable, Wire 12'

Accessories:

Additional Stem Lengths

**25-2078** (6"), **25-2079** (12")



### Mini Pendant

**60-5898** Mahogany Bronze with wrapped rope / Beige Linen Fabric Shade

(1) 60W A19 max. / Medium Base

Dimensions: Width 8", Height 16", Overall Height 54 1/8" Adjustable, Wire 12'

Accessories:

Additional Stem Lengths

**25-2078** (6"), **25-2079** (12")



### 3 Light Medium Pendant

**60-5899** Mahogany Bronze with wrapped rope / Beige Linen Fabric Shade / Etched Glass Diffuser

(3) 60W A19 max. / Medium Base

Dimensions: Width 17", Height 30 3/8", Overall Height 68 1/4" Adjustable, Wire 12'

Accessories:

Additional Stem Lengths

**25-2078** (6"), **25-2079** (12")



### 3 Light Small Pendant

**60-5897** Mahogany Bronze with wrapped rope / Beige Linen Fabric Shade

(3) 60W Type B max. / Candelabra Base

Dimensions: Width 12", Height 20 5/8", Overall Height 58 3/4" Adjustable, Wire 12'

Accessories:

Additional Stem Lengths

**25-2078** (6"), **25-2079** (12")



# SENECA



## 4 Light Large Pendant

**60-5841** Natural Brass / Almond Mesh  
Fabric Shade / Etched Glass Diffuser

(4) 60W A19 max. / Medium Base

Dimensions: Width 22", Height 22 $\frac{1}{8}$ ",  
Overall Height 60 $\frac{1}{8}$ " Adjustable, Wire 12'

Accessories:

Additional Stem Lengths

**25-4151** (6"), **25-4152** (12")





### Mini Pendant

**60-5843** Natural Brass / Almond Mesh Fabric Shade

(1) 60W A19 max. / Medium Base

Dimensions: Width 8", Height 16",  
Overall Height 54<sup>1</sup>/<sub>8</sub>" Adjustable, Wire 12'

Accessories:

Additional Stem Lengths

**25-4151** (6"), **25-4152** (12")



### 3 Light Medium Pendant

**60-5844** Natural Brass / Almond Mesh  
Fabric Shade / Etched Glass Diffuser

(3) 60W A19 max. / Medium Base

Dimensions: Width 17", Height 30<sup>3</sup>/<sub>8</sub>",  
Overall Height 68<sup>1</sup>/<sub>4</sub>" Adjustable, Wire 12'

Accessories:

Additional Stem Lengths

**25-4151** (6"), **25-4152** (12")



### 3 Light Small Pendant

**60-5842** Natural Brass / Almond Mesh Fabric Shade

(3) 60W Type B max. / Candelabra Base

Dimensions: Width 12", Height 20<sup>5</sup>/<sub>8</sub>",  
Overall Height 58<sup>3</sup>/<sub>4</sub>" Adjustable, Wire 12'

Accessories:

Additional Stem Lengths

**25-4151** (6"), **25-4152** (12")



# KRYS



## 4 Light Pendant

**60-5761** Polished Nickel / Clear Crystal Prisms

(4) 60W A19 max. / Medium Base

**S2423** 60W ST19 Vintage Lamps Included

Dimensions: Width 24<sup>5</sup>/<sub>8</sub>", Height 20<sup>1</sup>/<sub>2</sub>",  
Chain 48", Wire 12'

Accessories:

**25-4141** 3' Section of matching chain



#### 4 Light Trestle

**60-5765** Polished Nickel / Clear Crystal Prisms

(4) 60W A19 max. / Medium Base

**S2423** 60W ST19 Vintage Lamps Included

Dimensions: Length 36<sup>3</sup>/<sub>4</sub>", Width 10", Height 23<sup>1</sup>/<sub>8</sub>",  
Chain 48", Wire 12"

Accessories:

**25-4141** 3' Section of matching chain

# KRYS



## 4 Light Foyer

**60-5762** Polished Nickel / Clear Crystal Prisms

(4) 60W T9 max. / Candelabra Base

**S2420** 40W T9 Vintage Lamps Included

Dimensions: Width 14<sup>5</sup>/<sub>8</sub>", Height 26<sup>1</sup>/<sub>4</sub>",  
Chain 48", Wire 12'

Accessories:

**25-4141** 3' Section of matching chain



### 3 Light Semi-Flush

**60-5763** Polished Nickel / Clear Crystal Prisms

(3) 60W A19 max. / Medium Base

**S2423** 60W ST19 Vintage Lamps Included

Dimensions: Width 17<sup>3</sup>/<sub>4</sub>", Height 12<sup>1</sup>/<sub>8</sub>", Wire 12'

Accessories:

**25-4143** Pendant conversion kit

**25-4141** 3' Section of matching chain



### Short Prism Wall Sconce

**60-5766** Polished Nickel / Clear Crystal Prisms

(1) 60W A19 max. / Medium Base

**S2423** 60W ST19 Vintage Lamps Included

Dimensions: Width 8<sup>1</sup>/<sub>4</sub>", Height 12<sup>3</sup>/<sub>4</sub>", Extension 4<sup>3</sup>/<sub>4</sub>"



### Mini Pendant

**60-5764** Polished Nickel / Clear Crystal Prisms

(1) 60W A19 max. / Medium Base

**S2423** 60W ST19 Vintage Lamps Included

Dimensions: Width 7<sup>7</sup>/<sub>8</sub>", Height 50<sup>1</sup>/<sub>4</sub>" Adjustable, Wire 12'

Accessories:

Additional Stem Lengths

**25-4118** (6"), **25-4119** (12")



### Long Prism Wall Sconce

**60-5767** Polished Nickel / Clear Crystal Prisms

(1) 60W A19 max. / Medium Base

**S2423** 60W ST19 Vintage Lamps Included

Dimensions: Width 10<sup>1</sup>/<sub>4</sub>", Height 22<sup>3</sup>/<sub>4</sub>", Extension 5<sup>3</sup>/<sub>8</sub>"



# KRYS



## 4 Light Pendant

**60-5771** Aged Bronze / Clear Crystal Prisms

(4) 60W A19 max. / Medium Base

**S2423** 60W ST19 Vintage Lamps Included

Dimensions: Width 24<sup>5</sup>/<sub>8</sub>", Height 20<sup>1</sup>/<sub>2</sub>",  
Chain 48", Wire 12'

Accessories:

**25-4058** 3' Section of matching chain



### 4 Light Trestle

**60-5775** Aged Bronze / Clear Crystal Prisms

(4) 60W A19 max. / Medium Base

**S2423** 60W ST19 Vintage Lamps Included

Dimensions: Length 36<sup>3</sup>/<sub>4</sub>", Width 10", Height 23<sup>1</sup>/<sub>8</sub>",  
Chain 48", Wire 12'

Accessories:

**25-4058** 3' Section of matching chain

# KRYS



## 4 Light Foyer

**60-5772** Aged Bronze / Clear Crystal Prisms

(4) 60W T9 max. / Candelabra Base

**S2420** 60W T9 Vintage Lamps Included

Dimensions: Width 14<sup>5</sup>/<sub>8</sub>", Height 26<sup>1</sup>/<sub>4</sub>",  
Chain 48", Wire 12'

Accessories:

**25-4058** 3' Section of matching chain





### 3 Light Semi-Flush

**60-5773** Aged Bronze / Clear Crystal Prisms

(3) 60W A19 max. / Medium Base

**S2423** 60W ST19 Vintage Lamps Included

Dimensions: Width 17<sup>3</sup>/<sub>4</sub>", Height 12<sup>1</sup>/<sub>8</sub>", Wire 12'

Accessories:

**25-4097** Pendant conversion kit

**25-4058** 3' Section of matching chain



### Short Prism Wall Sconce

**60-5776** Aged Bronze / Clear Crystal Prisms

(1) 60W A19 max. / Medium Base

**S2423** 60W ST19 Vintage Lamps Included

Dimensions: Width 8<sup>1</sup>/<sub>4</sub>", Height 12<sup>3</sup>/<sub>4</sub>", Extension 4<sup>3</sup>/<sub>4</sub>"



### Mini Pendant

**60-5774** Aged Bronze / Clear Crystal Prisms

(1) 60W A19 max. / Medium Base

**S2423** 60W ST19 Vintage Lamps Included

Dimensions: Width 7<sup>7</sup>/<sub>8</sub>", Height 50<sup>1</sup>/<sub>4</sub>" Adjustable, Wire 12'

Accessories:

Additional Stem Lengths

**25-4066** (6"), **25-4067** (12")



### Long Prism Wall Sconce

**60-5777** Aged Bronze / Clear Crystal Prisms

(1) 60W A19 max. / Medium Base

**S2423** 60W ST19 Vintage Lamps Included

Dimensions: Width 10<sup>1</sup>/<sub>4</sub>", Height 22<sup>3</sup>/<sub>4</sub>", Extension 5<sup>3</sup>/<sub>8</sub>"



# SHERWOOD



## 8 Light Chandelier

**60-6128** Iron Black with Brushed Nickel Accents / Clear Glass

(8) 60W T9 max. / Medium Base  
40W T9 **S2426** Vintage Lamps Included

Dimensions: Width 25", Height 33<sup>3</sup>/<sub>8</sub>", Wire 12'

Accessories:

Additional Stem Lengths

**25-5892** (6"), **25-5893** (12")



### Open Cage Foyer

**60-6127** Iron Black with Brushed Nickel Accents / Clear Glass

(4) 60W T9 max. / Medium Base  
40W T9 **S2426** Vintage Lamps Included

Dimensions: Width 17", Height 35 1/2",  
Chain 48", Wire 12"

Accessories:

**25-6125** 3' Section of matching chain



### 2 Light Flush

**60-6126** Iron Black with Brushed Nickel Accents / Frosted Etched Glass

(2) 60W A19 max. / Medium Base

Dimensions: Width 14 3/4", Height 6 5/8"  
CUL damp location



### 4 Light Pendant

**60-6125** Iron Black with Brushed Nickel Accents / Frosted Etched Glass

(4) 60W A19 max. / Medium Base

Dimensions: Width 25 7/8", Height 27 1/8",  
Chain 48", Wire 12"

Accessories:

**25-6125** 3' Section of matching chain



# SHERWOOD



## 6 Light Island Pendant

**60-6124** Iron Black with Brushed Nickel Accents / Clear Glass

(6) 60W T9 max. / Medium Base  
40W T9 **S2426** Vintage Lamps Included

Dimensions: Length 38", Width 14", Height 24",  
Chain 48", Wire 12'

Accessories:

**25-6125** 3' Section of matching chain



### 2 Light Vanity

**60-6122** Iron Black with Brushed Nickel Accents / Clear Glass

(2) 60W T9 max. / Medium Base  
40W T9 **S2426** Vintage Lamps Included

Dimensions: Width 16", Height 10<sup>3</sup>/<sub>8</sub>", Extension 5<sup>7</sup>/<sub>8</sub>"  
CUL damp location



### 3 Light Vanity

**60-6123** Iron Black with Brushed Nickel Accents / Clear Glass

(3) 60W T9 max. / Medium Base  
40W T9 **S2426** Vintage Lamps Included

Dimensions: Width 24", Height 10<sup>3</sup>/<sub>8</sub>", Extension 8<sup>5</sup>/<sub>8</sub>"  
CUL damp location



### Wall Sconce

**60-6121** Iron Black with Brushed Nickel Accents / Clear Glass

(1) 60W T9 max. / Medium Base  
40W T9 **S2426** Vintage Lamp Included

Dimensions: Width 5<sup>1</sup>/<sub>2</sub>", Height 11<sup>5</sup>/<sub>8</sub>", Extension 5<sup>7</sup>/<sub>8</sub>"  
CUL damp location



### 4 Light Vanity

**60-6129** Iron Black with Brushed Nickel Accents / Clear Glass

(4) 60W T9 max. / Medium Base  
40W T9 **S2426** Vintage Lamps Included

Dimensions: Width 32", Height 10<sup>3</sup>/<sub>8</sub>", Extension 8<sup>5</sup>/<sub>8</sub>"  
CUL damp location



# BOXER



## 3 Light Island Pendant

**60-6133** Matte Black with Antique Silver Accents / Satin White Glass

(3) 100W A19 max. / Medium Base

Dimensions: Length 38", Width 5 1/8", Height 10 3/8", Overall Height 51" Adjustable, Wire 12'

Accessories:

Additional Stem Lengths

**25-6135** (6"), **25-6136** (12")



### Wall Sconce

**60-6131** Matte Black with Antique Silver Accents / Satin White Glass

(1) 100W A19 max. / Medium Base

Dimensions: Width 7", Height 10", Extension 6"



### Mini Pendant

**60-6135** Matte Black with Antique Silver Accents / Satin White Glass

(1) 100W A19 max. / Medium Base

Dimensions: Width 7 1/8", Height 8 5/8", Overall Height 46 5/8" Adjustable, Wire 12'

Accessories:

Additional Stem Lengths

**25-6135** (6"), **25-6136** (12")



### 2 Light Flush

**60-6132** Matte Black with Antique Silver Accents / Satin White Glass

(2) 60W A19 max. / Medium Base

Dimensions: Width 14", Height 6 1/4"



### 4 Light Pendant

**60-6134** Matte Black with Antique Silver Accents / Satin White Glass

(4) 100W A19 max. / Medium Base

Dimensions: Width 17", Height 17", Overall Height 57" Adjustable, Wire 12'

Accessories:

Additional Stem Lengths

**25-6135** (6"), **25-6136** (12")

# KETTLE



## 5 Light Oversized Pendant

**60-5895** Weathered Brass

(5) 60W A19 max. / Medium Base

**S2423** 60W ST19 Vintage Lamps Included

Dimensions: Width 30", Height 28" , Chain 48", Wire 12'

Accessories:

**25-5895** 3' Section of matching chain





### 3 Light Flush

**60-5893** Weathered Brass

(3) 60W A19 max. / Medium Base

**S2423** 60W ST19 Vintage Lamps Included

Dimensions: Width 12", Height 8"



### Wall Sconce

**60-5891** Weathered Brass

(1) 60W A19 max. / Medium Base

**S2423** 60W ST19 Vintage Lamps Included

Dimensions: Width 12", Height 8", Extension 5"

CUL damp location



### Mini Pendant

**60-5892** Weathered Brass

(1) 60W A19 max. / Medium Base

**S2423** 60W ST19 Vintage Lamps Included

Dimensions: Width 6", Height 8 1/2",

Overall Height 45" Adjustable, Wire 12'

Accessories:

Additional Stem Lengths

**25-5892** (6"), **25-5893** (12")



### 4 Light Pendant

**60-5894** Weathered Brass

(4) 60W A19 max. / Medium Base

**S2423** 60W ST19 Vintage Lamps Included

Dimensions: Width 20", Height 7",

Overall Height 41" Adjustable, Wire 12'

Accessories:

Additional Stem Lengths

**25-5892** (6"), **25-5893** (12")



# LAKE



## 4 Light Square Pendant

**60-5858** Iron Black with Brushed Nickel Accents

(4) 60W A19 max. / Medium Base

**S2423** 60W ST19 Vintage Lamps Included

Dimensions: Width 19", Height 27 1/2",  
Overall Height 65 3/4" Adjustable, Wire 12'

Accessories:

Additional Stem Lengths

**25-5892** (6"), **25-5893** (12")



### Wall Sconce

**60-5856** Iron Black with Brushed Nickel Accents  
 (1) 60W A19 max. / Medium Base  
**S2423** 60W ST19 Vintage Lamp Included  
 Dimensions: Width 8", Height 12", Extension 4 1/2"



### Mini Pendant

**60-5860** Iron Black with Brushed Nickel Accents  
 (1) 60W A19 max. / Medium Base  
**S2423** 60W ST19 Vintage Lamp Included  
 Dimensions: Width 8 1/8", Height 13 3/4",  
 Overall Height 51 7/8" Adjustable, Wire 12'  
 Accessories:  
 Additional Stem Lengths  
**25-5892** (6"), **25-5893** (12")




### 2 Light Square Pendant

**60-5857** Iron Black with Brushed Nickel Accents  
 (2) 60W A19 max. / Medium Base  
**S2423** 60W ST19 Vintage Lamps Included  
 Dimensions: Width 14", Height 20 1/2",  
 Overall Height 58 5/8" Adjustable, Wire 12'  
 Accessories:  
 Additional Stem Lengths  
**25-5892** (6"), **25-5893** (12")



### 4 Light Island Pendant

**60-5859** Iron Black with Brushed Nickel Accents  
 (4) 60W A19 max. / Medium Base  
**S2423** 60W ST19 Vintage Lamps Included  
 Dimensions: Length 36", Width 10", Height 11 1/4",  
 Overall Height 53" Adjustable, Wire 12'  
 Accessories:  
 Additional Stem Lengths  
**25-5892** (6"), **25-5893** (12")



# LAKE



## 4 Light Island Pendant

**60-5854** Bronze with Copper Accents

(4) 60W A19 max. / Medium Base

**S2423** 60W ST19 Vintage Lamps Included

Dimensions: Length 36", Width 10", Height 27½",  
Overall Height 53" Adjustable, Wire 12'

Additional Stem Lengths

25-4171 (6"), 25-4172 (12")



### Wall Sconce

**60-5851** Bronze with Copper Accents  
(1) 60W A19 max. / Medium Base  
**S2423** 60W ST19 Vintage Lamp Included  
Dimensions: Width 8", Height 12", Extension 4 1/2"



### Mini Pendant

**60-5855** Bronze with Copper Accents  
(1) 60W A19 max. / Medium Base  
**S2423** 60W ST19 Vintage Lamp Included  
Dimensions: Width 8 1/8", Height 13 3/4",  
Overall Height 51 7/8" Adjustable, Wire 12'  
Accessories:  
Additional Stem Lengths  
25-4171 (6"), 25-4172 (12")




### 4 Light Square Pendant

**60-5853** Bronze with Copper Accents  
(4) 60W A19 max. / Medium Base  
**S2423** 60W ST19 Vintage Lamps Included  
Dimensions: Width 19", Height 20 1/2",  
Overall Height 65 3/4" Adjustable, Wire 12'  
Additional Stem Lengths  
25-4171 (6"), 25-4172 (12")



### 2 Light Square Pendant

**60-5852** Bronze with Copper Accents  
(2) 60W A19 max. / Medium Base  
**S2423** 60W ST19 Vintage Lamps Included  
Dimensions: Width 14", Height 11 1/4",  
Overall Height 58 5/8" Adjustable, Wire 12'  
Additional Stem Lengths  
25-4171 (6"), 25-4172 (12")



# BANDIT



## 5 Light Chandelier

**60-5781** Brushed Nickel with Matte Black Accents

(5) 60W T9 max. / Medium Base

**S2422** 60W T9 Vintage Lamps Included

Dimensions: Width 26 5/8", Height 26 3/4",  
Overall Height 65 3/8" Adjustable, Wire 12'

Accessories:

Additional Stem Lengths

**25-2057** (6"), **25-2055** (12")



## 2 Light Wall Sconce

**60-5783** Brushed Nickel with Matte Black Accents

(2) 60W A19 max. / Medium Base

**S2422** 60W T9 Vintage Lamps Included

Dimensions: Width 5 5/8", Height 20", Extension 4"



bandit

## Mini Pendant

**60-5784** Brushed Nickel with Matte Black Accents

(1) 60W T9 max. / Medium Base

**S2422** 60W T9 Vintage Lamps Included

Dimensions: Width 4 3/8", Height 11 1/8",  
Overall Height 49 3/4" Adjustable, Wire 12'

Accessories:

Additional Stem Lengths

**25-2057** (6"), **25-2055** (12")

## 4 Light Island Pendant

**60-5782** Brushed Nickel with Matte Black Accents

(4) 60W T9 max. / Medium Base

**S2422** 60W T9 Vintage Lamps Included

Dimensions: Length 36", Width 4 3/8", Height 10 3/4",  
Overall Height 48 7/8" Adjustable, Wire 12'

Accessories:

Additional Stem Lengths

**25-2057** (6"), **25-2055** (12")



# BANDIT



## 5 Light Chandelier

**60-5786** Patina Bronze with Vintage Brass Accents

(5) 60W T9 max. / Medium Base

**S2422** 60W T9 Vintage Lamps Included

Dimensions: Width 26 5/8", Height 26 3/4",  
Overall Height 65 3/8" Adjustable, Wire 12'

Accessories:

Additional Stem Lengths

**25-5886** (6"), **25-5887** (12")





## 2 Light Wall Sconce

**60-5788** Patina Bronze with Vintage Brass Accents

(2) 60W A19 max. / Medium Base

**S2422** 60W T9 Vintage Lamps Included

Dimensions: Width 5 5/8", Height 20", Extension 4"



## Mini Pendant

**60-5789** Patina Bronze with Vintage Brass Accents

(1) 60W T9 max. / Medium Base

**S2422** 60W T9 Vintage Lamps Included

Dimensions: Width 4 3/8", Height 11 1/8",  
Overall Height 49 3/4" Adjustable, Wire 12'

Accessories:

Additional Stem Lengths

**25-5886** (6"), **25-5887** (12")



## 4 Light Island Pendant

**60-5787** Patina Bronze with Vintage Brass Accents

(4) 60W T9 max. / Medium Base

**S2422** 60W T9 Vintage Lamps Included

Dimensions: Length 36", Width 4 3/8", Height 10 3/4",  
Overall Height 48 7/8" Adjustable, Wire 12'

Accessories:

Additional Stem Lengths

**25-5886** (6"), **25-5887** (12")

bandit

# IRON



## 5 Light Hanging

**60-5795** Industrial Bronze

(5) 60W A19 max. / Medium Base

**S2423** 60W ST19 Vintage Lamps Included

Dimensions: Width 27", Fixed Height 17", Wire 12'

Accessories:



### 3 Light Vanity

**60-5793** Industrial Bronze

(3) 60W A19 max. / Medium Base

**S2423** 60W ST19 Vintage Lamps Included

Dimensions: Width 24½", Height 7"

CUL damp location



### 2 Light Vanity

**60-5792** Industrial Bronze

(2) 60W A19 max. / Medium Base

**S2423** 60W ST19 Vintage Lamps Included

Dimensions: Width 20", Height 7"

CUL damp location"



### 1 Light Vanity

**60-5791** Industrial Bronze

(1) 60W A19 max. / Medium Base

**S2423** 60W ST19 Vintage Lamps Included

Dimensions: Width 5", Height 7"

CUL damp location



### 4 Light Trestle

**60-5794** Industrial Bronze

(4) 60W A19 max. / Medium Base

**S2423** 60W ST19 Vintage Lamps Included

Dimensions: Width 27", Fixed Height 36½", Wire 12'



# FERN



## Large Vintage Glass Pendant

**60-5862** Polished Nickel / Clear Seeded Glass

(1) 40W A19 max. / Medium Base

**S2413** 40W ST19 Vintage Lamp Included

Dimensions: Width 9", Height 13<sup>3</sup>/<sub>4</sub>",  
Overall Height 51<sup>3</sup>/<sub>4</sub>" Adjustable, Wire 12'

Accessories:

Additional Stem Lengths

**25-4118** (6"), **25-4119** (12")

## Small Vintage Glass Pendant

**60-5861** Polished Nickel / Clear Seeded Glass

(1) 40W A19 max. / Medium Base

**S2413** 40W ST19 Vintage Lamp Included

Dimensions: Width 7<sup>1</sup>/<sub>2</sub>", Height 11<sup>5</sup>/<sub>8</sub>",  
Overall Height 49<sup>5</sup>/<sub>8</sub>" Adjustable, Wire 12'

Accessories:

Additional Stem Lengths

**25-4118** (6"), **25-4119** (12")



### Large Vintage Glass Pendant

**60-5867** Vintage Brass / Clear Seeded Glass

(1) 40W A19 max. / Medium Base

**S2413** 40W ST19 Vintage Lamp Included

Dimensions: Width 9", Height 13 3/4",  
Overall Height 51 3/4" Adjustable, Wire 12'

Accessories:

Additional Stem Lengths

**25-5867** (6"), **25-5868** (12")



### Small Vintage Glass Pendant

**60-5866** Vintage Brass / Clear Seeded Glass

(1) 40W A19 max. / Medium Base

**S2413** 40W ST19 Vintage Lamp Included

Dimensions: Width 7 1/2", Height 11 5/8",  
Overall Height 49 5/8" Adjustable, Wire 12'

Accessories:

Additional Stem Lengths

**25-5867** (6"), **25-5868** (12")



# MAXX



## Large Pendant

**60-5839** Polished Nickel  
(1) 60W A19 max. / Medium Base  
**S2423** 60W ST19 Vintage Lamp Included  
Dimensions: Width 10<sup>3</sup>/<sub>8</sub>", Height 13",  
Overall Height 50<sup>7</sup>/<sub>8</sub>" Adjustable, Wire 12'  
Accessories:  
Additional Stem Lengths  
**25-4118** (6"), **25-4119** (12")



## Small Pendant

**60-5837** Polished Nickel  
(1) 60W A19 max. / Medium Base  
**S2423** 60W ST19 Vintage Lamp Included  
Dimensions: Width 7<sup>1</sup>/<sub>4</sub>", Height 8<sup>1</sup>/<sub>2</sub>",  
Overall Height 46<sup>1</sup>/<sub>2</sub>" Adjustable, Wire 12'  
Accessories:  
Additional Stem Lengths  
**25-4118** (6"), **25-4119** (12")



## Medium Pendant

**60-5838** Polished Nickel  
(1) 60W A19 max. / Medium Base  
**S2423** 60W ST19 Vintage Lamp Included  
Dimensions: Width 8<sup>1</sup>/<sub>8</sub>", Height 9<sup>1</sup>/<sub>2</sub>",  
Overall Height 47<sup>3</sup>/<sub>8</sub>" Adjustable, Wire 12'  
Accessories:  
Additional Stem Lengths  
**25-4118** (6"), **25-4119** (12")



### Small Pendant

**60-5847** Mahogany Bronze  
(1) 60W A19 max. / Medium Base  
**S2423** 60W ST19 Vintage Lamp Included  
Dimensions: Width 7 $\frac{1}{4}$ ", Height 8 $\frac{1}{2}$ ",  
Overall Height 46 $\frac{1}{2}$ " Adjustable, Wire 12'  
Accessories:  
Additional Stem Lengths  
**25-2078** (6"), **25-2079** (12")



### Large Pendant

**60-5849** Mahogany Bronze  
(1) 60W A19 max. / Medium Base  
**S2423** 60W ST19 Vintage Lamp Included  
Dimensions: Width 10 $\frac{3}{8}$ ", Height 13",  
Overall Height 50 $\frac{7}{8}$ " Adjustable, Wire 12'  
Accessories:  
Additional Stem Lengths  
**25-2078** (6"), **25-2079** (12")



### Medium Pendant

**60-5848** Mahogany Bronze  
(1) 60W A19 max. / Medium Base  
**S2423** 60W ST19 Vintage Lamp Included  
Dimensions: Width 8 $\frac{1}{8}$ ", Height 9 $\frac{1}{2}$ ",  
Overall Height 47 $\frac{3}{8}$ " Adjustable, Wire 12'  
Accessories:  
Additional Stem Lengths  
**25-2078** (6"), **25-2079** (12")



Design is beautiful.  
Efficiency is beautiful.



Simplicity is beautiful.



In addition to providing the proper light in a space, a beautiful, and perfectly placed fixture, can make a statement. Whether strong or subtle, a successful lighting plan lets it be known that thought was given to, and has elevated, the entire project. Suddenly, everything seems well thought out and executed.

And beautiful, well-planned lighting doesn't just mean beautiful fixtures. There's a beauty to the simple LED utility fixture when put to its proper use. A closet becomes bright and open. A laundry room becomes easier to work in. A garage instantly becomes easier to navigate at night. And does it all while saving energy. It all has to do with the right fixture in the right place.

And it's all beautiful.



# CRATE LED



## Pendant Fixture

**62-893** Brushed Nickel / Gray Marbleized Acrylic Panels

(3) 13W LED Module / Dimmable

Dimensions: Width 20", Height 6", Overall Height 42" Adjustable, Wire 12'

Lumens: 3,120\*, CCT: 3000K, CRI: 80

Accessories:

Additional Stem Lengths

**25-2057** (6"), **25-2055** (12")



## Foyer Fixture

**62-894** Brushed Nickel / Gray Marbleized Acrylic Panels

(1) 32W LED Module / Dimmable

Dimensions: Width 14", Height 22", Overall Height 58" Adjustable, Wire 12'

Lumens: 2,500\*, CCT: 3000K, CRI: 80

Accessories:

Additional Stem Lengths

**25-2057** (6"), **25-2055** (12")



### 36" Light Vanity

**62-897** Brushed Nickel / Gray Marbleized Acrylic Panels  
(1) 39W LED Module / Dimmable  
Dimensions: Width 36", Height 5", Extension 2 1/2"  
Lumens: 3,120\*, CCT: 3000K, CRI: 80



### 14" Flush Fixture

**62-891** Brushed Nickel / Gray Marbleized Acrylic Panels  
(1) 32W LED Module / Dimmable  
Dimensions: Width 14", Height 6"  
Lumens: 2,500\*, CCT: 3000K, CRI: 80



### 24" Light Vanity

**62-896** Brushed Nickel / Gray Marbleized Acrylic Panels  
(1) 26W LED Module / Dimmable  
Dimensions: Width 24", Height 5", Extension 2 1/2"  
Lumens: 2,080\*, CCT: 3000K, CRI: 80



### 17" Flush Fixture

**62-892** Brushed Nickel / Gray Marbleized Acrylic Panels  
(3) 13W LED Module / Dimmable  
Dimensions: Width 17", Height 6"  
Lumens: 3,120\*, CCT: 3000K, CRI: 80



### 12" Light Vanity

**62-895** Brushed Nickel / Gray Marbleized Acrylic Panels  
(1) 13W LED Module / Dimmable  
Dimensions: Width 12", Height 5", Extension 2 1/2"  
Lumens: 1,040 \*, CCT: 3000K, CRI: 80



# TESS LED



## Two Tier – 9 Light Chandelier

**62-810** Brushed Nickel / Frosted Fluted Glass

(9) 8.5W LED Modules / Dimmable

Dimensions: Width 33<sup>3</sup>/<sub>8</sub>", Height 30", Chain 72", Wire 12'

Lumens: 7,200\*, CCT: 3000K, CRI: 80

Accessories:

**25-4052** 3' Section of matching chain



### 5 Light Chandelier

**62-805** Brushed Nickel / Frosted Fluted Glass

(5) 8.5W LED Modules / Dimmable

Dimensions: Width 27<sup>3</sup>/<sub>8</sub>", Height 23<sup>1</sup>/<sub>8</sub>", Chain 48", Wire 12'

Lumens: 4,000\*, CCT: 3000K, CRI: 80

Accessories:

**25-1069** 3' Section of matching chain



### 1 Light Mini Pendant

**62-806** Brushed Nickel / Frosted Fluted Glass

(1) 8.5W LED Module / Dimmable

Dimensions: Width 7<sup>1</sup>/<sub>8</sub>", Height 45<sup>1</sup>/<sub>8</sub>"  
Adjustable, Wire 12'

Lumens: 800\*, CCT: 3000K, CRI: 80

Accessories:

Additional Stem Lengths

**25-2057** (6"), **25-2055** (12")

# TESS LED



## 4 Light Foyer

**62-804** Brushed Nickel / Frosted Fluted Glass

(4) 8.5W LED Modules / Dimmable

Dimensions: Width 22<sup>5</sup>/<sub>8</sub>", Height 23<sup>7</sup>/<sub>8</sub>",  
Chain 48", Wire 12'

Lumens: 3,200\*, CCT: 3000K, CRI: 80

Accessories:

**25-1069** 3' Section of matching chain



## 3 Light Pendant

**62-807** Brushed Nickel / Frosted Fluted Glass /  
White Organza Shade

(3) 8.5W LED Modules / Dimmable

Dimensions: Width 24", Height 22<sup>7</sup>/<sub>8</sub>",  
Chain 48", Wire 12'

Lumens: 2,400\*, CCT: 3000K, CRI: 80

Accessories:

**25-1069** 3' Section of matching chain



### 1 Light Vanity

**62-801** Brushed Nickel / Frosted Fluted Glass  
(1) 8.5W LED Module / Dimmable  
Dimensions: Width 7<sup>1</sup>/<sub>8</sub>", Height 10", Extension 8<sup>3</sup>/<sub>4</sub>"  
Lumens: 800 \*, CCT: 3000K, CRI: 80



### Flush Dome

**62-809** Brushed Nickel / Frosted Fluted Glass  
(1) 18W LED Module / Dimmable  
Dimensions: Width 13", Height 7"  
Lumens: 1,430\*, CCT: 3000K, CRI: 80



### 2 Light Vanity

**62-802** Brushed Nickel / Frosted Fluted Glass  
(2) 8.5W LED Modules / Dimmable  
Dimensions: Width 16", Height 10<sup>1</sup>/<sub>8</sub>", Extension 8<sup>3</sup>/<sub>4</sub>"  
Lumens: 1,600\*, CCT: 3000K, CRI: 80



### Semi-Flush Dome

**62-808** Brushed Nickel / Frosted Fluted Glass  
(2) 8.5W LED Modules / Dimmable  
Dimensions: Width 12<sup>7</sup>/<sub>8</sub>", Height 9<sup>3</sup>/<sub>8</sub>", Wire 12'  
Lumens: 1,600\*, CCT: 3000K, CRI: 80

Accessories:

**25-1403** Pendant conversion kit

**25-1069** 3' Section of matching chain



### 3 Light Vanity

**62-803** Brushed Nickel / Frosted Fluted Glass  
(3) 8.5W LED Modules / Dimmable  
Dimensions: Width 25<sup>3</sup>/<sub>8</sub>", Height 10<sup>1</sup>/<sub>8</sub>", Extension 8<sup>3</sup>/<sub>4</sub>"  
Lumens: 2,400\*, CCT: 3000K, CRI: 80

# TESS LED



## Two Tier – 9 Light Chandelier

62-910 Aged Bronze / Frosted Fluted Glass

(9) 8.5W LED Modules / Dimmable

Dimensions: Width 33<sup>3</sup>/<sub>8</sub>", Height 30", Chain 72", Wire 12'

Lumens: 7,200\*, CCT: 3000K, CRI: 80

Accessories:

25-4065 3' Section of matching chain





### 5 Light Chandelier

**62-905** Aged Bronze / Frosted Fluted Glass

(5) 8.5W LED Modules / Dimmable

Dimensions: Width 27<sup>3</sup>/<sub>8</sub>", Height 23<sup>1</sup>/<sub>8</sub>", Chain 48", Wire 12'

Lumens: 4,000\*, CCT: 3000K, CRI: 80

Accessories:

**25-4058** 3' Section of matching chain



### 1 Light Mini Pendant

**62-906** Aged Bronze / Frosted Fluted Glass

(1) 8.5W LED Module / Dimmable

Dimensions: Width 7<sup>1</sup>/<sub>8</sub>", Height 45<sup>1</sup>/<sub>8</sub>"  
Adjustable, Wire 12'

Lumens: 800\*, CCT: 3000K, CRI: 80

Accessories:

Additional Stem Lengths

**25-4066** (6"), **25-4067** (12")

# TESS LED



## 4 Light Foyer

**62-904** Aged Bronze / Frosted Fluted Glass

(4) 8.5W LED Modules / Dimmable

Dimensions: Width 22<sup>5</sup>/<sub>8</sub>", Height 23<sup>7</sup>/<sub>8</sub>",  
Chain 48", Wire 12'

Lumens: 3,200\*, CCT: 3000K, CRI: 80

Accessories:

**25-4058** 3' Section of matching chain



## 3 Light Pendant

**62-907** Aged Bronze / Frosted Fluted Glass /  
Beige Organza Shade

(3) 8.5W LED Modules / Dimmable

Dimensions: Width 24", Height 22<sup>7</sup>/<sub>8</sub>",  
Chain 48", Wire 12'

Lumens: 2,400\*, CCT: 3000K, CRI: 80

Accessories:

**25-4058** 3' Section of matching chain



### 1 Light Vanity

**62-901** Aged Bronze / Frosted Fluted Glass  
(1) 8.5W LED Module / Dimmable  
Dimensions: Width 7<sup>1</sup>/<sub>8</sub>", Height 10", Extension 8<sup>3</sup>/<sub>4</sub>"  
Lumens: 800\*, CCT: 3000K, CRI: 80



### Flush Dome

**62-909** Aged Bronze / Frosted Fluted Glass  
(1) 18W LED Module / Dimmable  
Dimensions: Width 13", Height 7"  
Lumens: 1,430\*, CCT: 3000K, CRI: 80



### 2 Light Vanity

**62-902** Aged Bronze / Frosted Fluted Glass  
(2) 8.5W LED Modules / Dimmable  
Dimensions: Width 16", Height 10<sup>1</sup>/<sub>8</sub>", Extension 8<sup>3</sup>/<sub>4</sub>"  
Lumens: 1,600\*, CCT: 3000K, CRI: 80



### Semi-Flush Dome

**62-908** Aged Bronze / Frosted Fluted Glass  
(2) 8.5W LED Modules / Dimmable  
Dimensions: Width 12<sup>7</sup>/<sub>8</sub>", Height 9<sup>3</sup>/<sub>8</sub>", Wire 12'  
Lumens: 1,600\*, CCT: 3000K, CRI: 80

Accessories:

**25-4097** Pendant conversion kit

**25-4058** 3' Section of matching chain



### 3 Light Vanity

**62-903** Aged Bronze / Frosted Fluted Glass  
(3) 8.5W LED Modules / Dimmable  
Dimensions: Width 25<sup>3</sup>/<sub>8</sub>", Height 10<sup>1</sup>/<sub>8</sub>", Extension 8<sup>3</sup>/<sub>4</sub>"  
Lumens: 2,400\*, CCT: 3000K, CRI: 80



# THORN LED



## Large LED Pendant

**62-842** Brushed Nickel with White Accents  
(1) 15W LED Panel / Dimmable  
Dimensions: Width 9", Height 24",  
Overall Height 60" Adjustable, Wire 12'  
Lumens: 1,190\*, CCT: 3000K, CRI: 80  
Accessories:  
Additional Stem Lengths  
**25-2057** (6"), **25-2055** (12")



## Small LED Pendant

**62-841** Brushed Nickel with White Accents  
(1) 15W LED Panel / Dimmable  
Dimensions: Width 6 1/2", Height 16",  
Overall Height 52" Adjustable, Wire 12'  
Lumens: 1,190\*, CCT: 3000K, CRI: 80  
Accessories:  
Additional Stem Lengths  
**25-2057** (6"), **25-2055** (12")



### Large LED Pendant

**62-847** Bronze with Copper Accents  
(1) 15W LED Panel / Dimmable  
Dimensions: Width 9", Height 24",  
Overall Height 60" Adjustable, Wire 12'  
Lumens: 1,190\*, CCT: 3000K, CRI: 80  
Accessories:  
Additional Stem Lengths  
**25-4171** (6"), **25-4172** (12")



### Small LED Pendant

**62-846** Bronze with Copper Accents  
(1) 15W LED Panel / Dimmable  
Dimensions: Width 6 1/2", Height 16",  
Overall Height 52" Adjustable, Wire 12'  
Lumens: 1,190\*, CCT: 3000K, CRI: 80  
Accessories:  
Additional Stem Lengths  
**25-4171** (6"), **25-4172** (12")



# DORAL LED



## Large LED Pendant

**62-852** Brushed Nickel with White Accents

(1) 15W LED Panel / Dimmable

Dimensions: Width 14", Height 11",  
Overall Height 47" Adjustable, Wire 12'

Lumens: 1,190\*, CCT: 3000K, CRI: 80

Accessories:

Additional Stem Lengths

**25-2057** (6"), **25-2055** (12")



## Small LED Pendant

**62-851** Brushed Nickel with White Accents

(1) 12W LED Panel / Dimmable

Dimensions: Width 10", Height 8",  
Overall Height 42" Adjustable, Wire 12'

Lumens: 950\*, CCT: 3000K, CRI: 80

Accessories:

Additional Stem Lengths

**25-2057** (6"), **25-2055** (12")



### Large LED Pendant

**62-857** Bronze with Copper Accents  
(1) 15W LED Panel / Dimmable  
Dimensions: Width 14", Height 11",  
Overall Height 47" Adjustable, Wire 12'  
Lumens: 1,190\*, CCT: 3000K, CRI: 80  
Accessories:  
Additional Stem Lengths  
**25-4171** (6"), **25-4172** (12")



### Small LED Pendant

**62-856** Bronze with Copper Accents  
(1) 12W LED Panel / Dimmable  
Dimensions: Width 10", Height 8",  
Overall Height 42" Adjustable, Wire 12'  
Lumens: 950\*, CCT: 3000K, CRI: 80  
Accessories:  
Additional Stem Lengths  
**25-4171** (6"), **25-4172** (12")



# THRUST LED



## Large LED Pendant

**62-862** Brushed Nickel with Black and White Accents

(1) 15W LED Panel / Dimmable

Dimensions: Width 10 1/2", Height 14 1/2",  
Overall Height 51" Adjustable, Wire 12'

Lumens: 1,190\*, CCT: 3000K, CRI: 80

Accessories:

Additional Stem Lengths

**25-5861** (6"), **25-5862** (12")



## Small LED Pendant

**62-861** Brushed Nickel with Black and White Accents

(1) 12W LED Panel / Dimmable

Dimensions: Width 7", Height 9",  
Overall Height 45" Adjustable, Wire 12'

Lumens: 950\*, CCT: 3000K, CRI: 80

Accessories:

Additional Stem Lengths

**25-5861** (6"), **25-5862** (12")





### Large LED Pendant

**62-867** Bronze with Copper Accents  
(1) 15W LED Panel / Dimmable  
Dimensions: Width 10½", Height 14½",  
Overall Height 51" Adjustable, Wire 12'  
Lumens: 1,190\*, CCT: 3000K, CRI: 80  
Accessories:  
Additional Stem Lengths  
**25-4171** (6"), **25-4172** (12")



### Small LED Pendant

**62-866** Bronze with Copper Accents  
(1) 12W LED Panel / Dimmable  
Dimensions: Width 7", Height 9",  
Overall Height 45" Adjustable, Wire 12'  
Lumens: 950\*, CCT: 3000K, CRI: 80  
Accessories:  
Additional Stem Lengths  
**25-4171** (6"), **25-4172** (12")



# TEX LED



## Large LED Pendant

**62-882** Brushed Nickel / Black Mesh  
(1) 15W LED Panel / Dimmable  
Dimensions: Width 13 1/2", Height 11 1/2",  
Overall Height 48" Adjustable, Wire 12'  
Lumens: 1,190\*, CCT: 3000K, CRI: 80  
Accessories:  
Additional Stem Lengths  
**25-2057** (6"), **25-2055** (12")



## Small LED Pendant

**62-881** Brushed Nickel / Black Mesh  
(1) 12W LED Panel / Dimmable  
Dimensions: Width 8 1/4", Height 8",  
Overall Height 44" Adjustable, Wire 12'  
Lumens: 950\*, CCT: 3000K, CRI: 80  
Accessories:  
Additional Stem Lengths  
**25-2057** (6"), **25-2055** (12")



### Large LED Pendant

**62-887** Bronze / Copper Mesh  
(1) 15W LED Panel / Dimmable  
Dimensions: Width 13 1/2", Height 11 1/2",  
Overall Height 48" Adjustable, Wire 12'  
Lumens: 1,190\*, CCT: 3000K, CRI: 80  
Accessories:  
Additional Stem Lengths  
**25-4171** (6"), **25-4172** (12")



### Small LED Pendant

**62-886** Bronze / Copper Mesh  
(1) 12W LED Panel / Dimmable  
Dimensions: Width 8 1/4", Height 8",  
Overall Height 44" Adjustable, Wire 12'  
Lumens: 950\*, CCT: 3000K, CRI: 80  
Accessories:  
Additional Stem Lengths  
**25-4171** (6"), **25-4172** (12")

tex LED

# VESSEL LED



## LED Mini Pendant

**62-837** Brushed Nickel with White Accents

(1) 12W LED Panel / Dimmable

Dimensions: Width 6", Height 8½", 12' Black SVT cable

Lumens: 950\*, CCT: 3000K, CRI: 80



### LED Mini Pendant

**62-838** Bronze with Copper Accents

(1) 12W LED Panel / Dimmable

Dimensions: Width 6", Height 8 1/2", 12' Black SVT cable

Lumens: 950\*, CCT: 3000K, CRI: 80

vessel LED

DEL  
LED




### LED Mini Pendant

**62-877** Brushed Nickel / White Opal Glass  
(1) 12W LED Panel / Dimmable  
Dimensions: Width 6<sup>3</sup>/<sub>4</sub>", Height 9<sup>1</sup>/<sub>4</sub>",  
12' Black SVT cable  
Lumens: 950\*, CCT: 3000K, CRI: 80



### LED Mini Pendant

**62-878** Brushed Nickel / Clear Crackle Glass  
(1) 12W LED Panel / Dimmable  
Dimensions: Width 6<sup>3</sup>/<sub>4</sub>", Height 9<sup>1</sup>/<sub>4</sub>",  
12' Black SVT cable  
Lumens: 950\*, CCT: 3000K, CRI: 80




### LED Mini Pendant

**62-879** Brushed Nickel / Antique Gold Glass  
(1) 12W LED Panel / Dimmable  
Dimensions: Width 6<sup>3</sup>/<sub>4</sub>", Height 9<sup>1</sup>/<sub>4</sub>",  
12' Black SVT cable  
Lumens: 950\*, CCT: 3000K, CRI: 80




### LED Mini Pendant

**62-888** Brushed Nickel / Mirrored Glass  
(1) 12W LED Panel / Dimmable  
Dimensions: Width 6<sup>3</sup>/<sub>4</sub>", Height 9<sup>1</sup>/<sub>4</sub>",  
12' Black SVT cable  
Lumens: 950\*, CCT: 3000K, CRI: 80



### LED Mini Pendant

**62-889** Brushed Nickel / Copper Glass  
(1) 12W LED Panel / Dimmable  
Dimensions: Width 6<sup>3</sup>/<sub>4</sub>", Height 9<sup>1</sup>/<sub>4</sub>",  
12' Black SVT cable  
Lumens: 950\*, CCT: 3000K, CRI: 80



# PULSE LED



## LED Mini Pendant

**62-954** Brushed Nickel / Mirrored Glass  
(1) 12W LED Panel / Dimmable  
Dimensions: Width 3", Height 10",  
12' Black SVT cable  
Lumens: 950\*, CCT: 3000K, CRI: 80



## LED Mini Pendant

**62-953** Brushed Nickel / White Opal Glass  
(1) 12W LED Panel / Dimmable  
Dimensions: Width 3", Height 10",  
12' Black SVT cable  
Lumens: 950\*, CCT: 3000K, CRI: 80





### LED Mini Pendant

**62-952** Brushed Nickel / Clear Crackle Glass  
(1) 12W LED Panel / Dimmable  
Dimensions: Width 3", Height 10",  
12' Black SVT cable  
Lumens: 950\*, CCT: 3000K, CRI: 80



### LED Mini Pendant

**62-951** Brushed Nickel / Clear Seeded Glass  
(1) 12W LED Panel / Dimmable  
Dimensions: Width 3", Height 10",  
12' Black SVT cable  
Lumens: 950\*, CCT: 3000K, CRI: 80



### LED Mini Pendant

**62-955** Brushed Nickel / Copper Glass  
(1) 12W LED Panel / Dimmable  
Dimensions: Width 3", Height 10",  
12' Black SVT cable  
Lumens: 950\*, CCT: 3000K, CRI: 80



# HAWK LED



## Pivoting Head Wall Sconce

**62-993** Textured Black  
(1) 15W LED Module / Dimmable  
Dimensions: Width 6 1/2", Height 5", Extension 7 5/8"  
Lumens: 1,190\*, CCT: 3000K, CRI: 90  
CUL damp location



## Pivoting Head Wall Sconce

**62-994** Brushed Nickel  
(1) 15W LED Module / Dimmable  
Dimensions: Width 6 1/2", Height 5", Extension 7 5/8"  
Lumens: 1,190\*, CCT: 3000K, CRI: 90  
CUL damp location



## Pivoting Head Wall Sconce

**62-992** White  
(1) 15W LED Module / Dimmable  
Dimensions: Width 6 1/2", Height 5", Extension 7 5/8"  
Lumens: 1,190\*, CCT: 3000K, CRI: 90  
CUL damp location



Pivoting Head Pendant

**62-996** Textured Black

(1) 15W LED Module / Dimmable

Dimensions: Width 6 1/2", Height 2 1/2",  
Wire and Cable 12'

Lumens: 1,190\*, CCT: 3000K, CRI: 90




Pivoting Head Pendant

**62-995** White

(1) 15W LED Module / Dimmable

Dimensions: Width 6 1/2", Height 2 1/2",  
Wire and Cable 12'

Lumens: 1,190\*, CCT: 3000K, CRI: 90



Pivoting Head Pendant

**62-997** Brushed Nickel

(1) 15W LED Module / Dimmable

Dimensions: Width 6 1/2", Height 2 1/2",  
Wire and Cable 12'

Lumens: 1,190\*, CCT: 3000K, CRI: 90



\*Lumens measured at LED source

# DECOR LED



## Filigree Flush

**62-989** Polished Nickel / White Fabric Shade / Acrylic Diffuser

(1) 16.5W LED Module / Dimmable

Dimensions: Width 15", Height 4 1/4"

Lumens: 1,200\*, CCT: 3000K, CRI: 90



## Filigree Flush

**62-987** Natural Brass / White Fabric Shade / Acrylic Diffuser

(1) 16.5W LED Module / Dimmable

Dimensions: Width 15", Height 4 1/4"

Lumens: 1,200\*, CCT: 3000K, CRI: 90



### Filigree Flush

**62-988** Polished Nickel / White Fabric Shade / Acrylic Diffuser  
(1) 16.5W LED Module / Dimmable  
Dimensions: Width 15", Height 4 1/4"  
Lumens: 1,200\*, CCT: 3000K, CRI: 90



### Fabric Drum Flush

**62-990** White Fabric Shade / Acrylic Diffuser  
(1) 16.5W LED Module / Dimmable  
Dimensions: Width 15", Height 4 1/4"  
Lumens: 1,200\*, CCT: 3000K, CRI: 90



### Filigree Flush

**62-986** Natural Brass / White Fabric Shade / Acrylic Diffuser  
(1) 16.5W LED Module / Dimmable  
Dimensions: Width 15", Height 4 1/4"  
Lumens: 1,200\*, CCT: 3000K, CRI: 90



### Fabric Drum Flush

**62-985** Beige Fabric Shade / Acrylic Diffuser  
(1) 16.5W LED Module / Dimmable  
Dimensions: Width 15", Height 4 1/4"  
Lumens: 1,200\*, CCT: 3000K, CRI: 90



# GRILL LED



## Wall Sconce

**62-871** Polished Nickel / White Acrylic Lens  
(1) 13W LED Module / Dimmable  
Dimensions: Width 4", Height 12", Extension 3"  
Lumens: 1,040 \*, CCT: 3000K, CRI: 80



## Vanity

**62-872** Polished Nickel / White Acrylic Lens  
(1) 26W LED Module / Dimmable  
Dimensions: Width 4", Height 24", Extension 3"  
Lumens: 2,080\*, CCT: 3000K, CRI: 80



## Vanity

**62-875** Polished Nickel / White Acrylic Lens  
(1) 39W LED Module / Dimmable  
Dimensions: Length 36", Width 4", Extension 3"  
Lumens: 3,120\*, CCT: 3000K, CRI: 80



### Wall Sconce

**62-873** Aged Bronze / White Acrylic Lens  
(1) 13W LED Module / Dimmable  
Dimensions: Width 4", Height 12", Extension 3"  
Lumens: 1,040 \*, CCT: 3000K, CRI: 80



### Vanity

**62-874** Aged Bronze / White Acrylic Lens  
(1) 26W LED Module / Dimmable  
Dimensions: Width 4", Height 24", Extension 3"  
Lumens: 2,080\*, CCT: 3000K, CRI: 80



### Vanity

**62-876** Aged Bronze / White Acrylic Lens  
(1) 39W LED Module / Dimmable  
Dimensions: Length 36", Width 4", Extension 3"  
Lumens: 3,120\*, CCT: 3000K, CRI: 80



# PACE LED



## Wall Sconce

**62-911** Brushed Nickel / White Acrylic Lens  
(1) 13W LED Module / Dimmable  
Dimensions: Width 5", Height 12", Extension 3 1/4"  
Lumens: 1,040 \*, CCT: 3000K, CRI: 80



## Vanity

**62-912** Brushed Nickel / White Acrylic Lens  
(1) 26W LED Module / Dimmable  
Dimensions: Width 5", Height 24", Extension 3 1/4"  
Lumens: 2,080\*, CCT: 3000K, CRI: 80



## Vanity

**62-915** Brushed Nickel / White Acrylic Lens  
(1) 39W LED Module / Dimmable  
Dimensions: Length 36", Width 5", Extension 3 1/4"  
Lumens: 3,120\*, CCT: 3000K, CRI: 80





### Wall Sconce

**62-913** Aged Bronze / White Acrylic Lens  
(1) 13W LED Module / Dimmable  
Dimensions: Width 5", Height 12", Extension 3 1/4"  
Lumens: 1,040 \*, CCT: 3000K, CRI: 80



### Vanity

**62-914** Aged Bronze / White Acrylic Lens  
(1) 26W LED Module / Dimmable  
Dimensions: Width 5", Height 24", Extension 3 1/4"  
Lumens: 2,080\*, CCT: 3000K, CRI: 80



### Vanity

**62-916** Aged Bronze / White Acrylic Lens  
(1) 39W LED Module / Dimmable  
Dimensions: Length 36", Width 5", Extension 3 1/4"  
Lumens: 3,120\*, CCT: 3000K, CRI: 80



# LOOP LED



## Wall Sconce

**62-921** Brushed Nickel / White Acrylic Lens  
(1) 13W LED Module / Dimmable  
Dimensions: Width 4", Height 12", Extension 3 1/8"  
Lumens: 1,040 \*, CCT: 3000K, CRI: 80



## Vanity

**62-922** Brushed Nickel / White Acrylic Lens  
(1) 26W LED Module / Dimmable  
Dimensions: Width 4", Height 24", Extension 3 1/8"  
Lumens: 2,080\*, CCT: 3000K, CRI: 80




## Vanity

**62-925** Brushed Nickel / White Acrylic Lens  
(1) 39W LED Module / Dimmable  
Dimensions: Length 36", Width 4", Extension 3 1/8"  
Lumens: 3,120\*, CCT: 3000K, CRI: 80



### Wall Sconce

**62-923** Aged Bronze / White Acrylic Lens  
(1) 13W LED Module / Dimmable  
Dimensions: Width 4", Height 12", Extension 3 1/8"  
Lumens: 1,040 \*, CCT: 3000K, CRI: 80



### Vanity

**62-924** Aged Bronze / White Acrylic Lens  
(1) 26W LED Module / Dimmable  
Dimensions: Width 4", Height 24", Extension 3 1/8"  
Lumens: 2,080\*, CCT: 3000K, CRI: 80



### Vanity

**62-926** Aged Bronze / White Acrylic Lens  
(1) 39W LED Module / Dimmable  
Dimensions: Length 36", Width 4", Extension 3 1/8"  
Lumens: 3,120\*, CCT: 3000K, CRI: 80



# SLICE LED



## Wall Sconce

**62-931** Polished Nickel / White Acrylic Lens  
(1) 13W LED Module / Dimmable  
Dimensions: Width 4 1/2", Height 12", Extension 3"  
Lumens: 1,040 \*, CCT: 3000K, CRI: 80



## Vanity

**62-932** Polished Nickel / White Acrylic Lens  
(1) 26W LED Module / Dimmable  
Dimensions: Width 4 1/2", Height 24", Extension 3"  
Lumens: 2,080\*, CCT: 3000K, CRI: 80



## Vanity

**62-935** Polished Nickel / White Acrylic Lens  
(1) 39W LED Module / Dimmable  
Dimensions: Length 36", Width 4 1/2", Extension 3"  
Lumens: 3,120\*, CCT: 3000K, CRI: 80



### Wall Sconce

**62-933** Aged Bronze / White Acrylic Lens  
(1) 13W LED Module / Dimmable  
Dimensions: Width 4½", Height 12", Extension 3"  
Lumens: 1,040 \*, CCT: 3000K, CRI: 80



### Wall Sconce

**62-934** Aged Bronze / White Acrylic Lens  
(1) 26W LED Module / Dimmable  
Dimensions: Width 4½", Height 24", Extension 3"  
Lumens: 2,080\*, CCT: 3000K, CRI: 80



### Vanity

**62-936** Aged Bronze / White Acrylic Lens  
(1) 39W LED Module / Dimmable  
Dimensions: Length 36", Width 4½", Extension 3"  
Lumens: 3,120\*, CCT: 3000K, CRI: 80



# BUNGALOW LED



## Large Wall Lantern

**62-943** Mahogany Bronze / Etched Seeded Glass  
(1) 15W LED Light Engine / Dimmable  
Dimensions: Width 11", Height 15 1/2", Extension 11 7/8"  
Lumens: 1,190\*, CCT: 3000K, CRI: 80



### Flush Lantern

**62-944** Mahogany Bronze / Etched Seeded Glass  
(1) 15W LED Panel / Dimmable  
Dimensions: Width 13", Height 4 1/8"  
Lumens: 1,190\*, CCT: 3000K, CRI: 80



### Hanging Lantern

**62-946** Mahogany Bronze / Etched Seeded Glass  
(1) 15W LED Light Engine / Dimmable  
Dimensions: Width 11", Height 16 1/2",  
Chain 48", Wire 12"  
Lumens: 1,190\*, CCT: 3000K, CRI: 80  
Accessories:  
**25-4225** 3' Section of matching chain



### Small Wall Lantern

**62-941** Mahogany Bronze / Etched Seeded Glass  
(1) 12W LED Light Engine / Dimmable  
Dimensions: Width 7 1/2", Height 11 1/8", Extension 8 1/4"  
Lumens: 950\*, CCT: 3000K, CRI: 80



### Medium Wall Lantern

**62-942** Mahogany Bronze / Etched Seeded Glass  
(1) 15W LED Light Engine / Dimmable  
Dimensions: Width 9", Height 12 7/8", Extension 9 3/4"  
Lumens: 1,190\*, CCT: 3000K, CRI: 80



### Post Lantern

**62-945** Mahogany Bronze / Etched Seeded Glass  
(1) 15W LED Light Engine / Dimmable  
Dimensions: Width 11", Height 7 1/2"  
Lumens: 1,190\*, CCT: 3000K, CRI: 80  
Accessories:  
**25-5945** Mahogany Bronze pier mount base

# ESSEX LED



## Large Wall Lantern

**62-822** Sterling Black / Etched Glass

(1) 12W LED Light Engine / Dimmable

Dimensions: Width 8 $\frac{1}{4}$ ", Height 16 $\frac{7}{8}$ ", Extension 9 $\frac{5}{8}$ "

Lumens: 950\*, CCT: 3000K, CRI: 80





### Flush Lantern

**62-823** Sterling Black / Etched Glass  
(1) 15W LED Panel / Dimmable  
Dimensions: Width 11", Height 5 1/4"  
Lumens: 1,190\*, CCT: 3000K, CRI: 80



### Hanging Lantern

**62-824** Sterling Black / Etched Glass  
(1) 12W LED Light Engine / Dimmable  
Dimensions: Width 8 1/4", Height 15 3/8",  
Chain 48", Wire 12"  
Lumens: 950\*, CCT: 3000K, CRI: 80  
Accessories:  
**25-5826** 3' Section of matching chain



### Small Wall Lantern

**62-821** Sterling Black / Etched Glass  
(1) 12W LED Light Engine / Dimmable  
Dimensions: Width 6 1/2", Height 14", Extension 7 3/4"  
Lumens: 950\*, CCT: 3000K, CRI: 80



### Post Lantern

**62-825** Sterling Black / Etched Glass  
(1) 12W LED Light Engine / Dimmable  
Dimensions: Width 8 1/4", Height 18 1/8"  
Lumens: 950\*, CCT: 3000K, CRI: 80  
Accessories:  
**25-5825** Sterling Black pier mount base



# WINTHROP LED



## Large Wall Lantern

**62-832** Iron Black / Etched Water Glass

(1) 15W LED Light Engine / Dimmable

Dimensions: Width 7½", Height 19½", Extension 9¼"

Lumens: 1,190\*, CCT: 3000K, CRI: 80



### Flush Lantern

**62-833** Iron Black / Etched Water Glass  
(1) 15W LED Panel / Dimmable  
Dimensions: Width 11", Height 5<sup>3</sup>/<sub>8</sub>"  
Lumens: 1,190\*, CCT: 3000K, CRI: 80



### Hanging Lantern

**62-834** Iron Black / Etched Water Glass  
(1) 15W LED Light Engine / Dimmable  
Dimensions: Width 7<sup>1</sup>/<sub>2</sub>", Height 18<sup>5</sup>/<sub>8</sub>",  
Chain 48", Wire 12"  
Lumens: 1,190\*, CCT: 3000K, CRI: 80  
Accessories:  
**25-5836** 3' Section of matching chain



### Small Wall Lantern

**62-831** Iron Black / Etched Water Glass  
(1) 12W LED Light Engine / Dimmable  
Dimensions: Width 5<sup>1</sup>/<sub>2</sub>", Height 14<sup>3</sup>/<sub>4</sub>", Extension 7<sup>3</sup>/<sub>8</sub>"  
Lumens: 950\*, CCT: 3000K, CRI: 80



### Post Lantern

**62-835** Iron Black / Etched Water Glass  
(1) 15W LED Light Engine / Dimmable  
Dimensions: Width 7<sup>1</sup>/<sub>2</sub>", Height 21<sup>1</sup>/<sub>4</sub>"  
Lumens: 1,190\*, CCT: 3000K, CRI: 80  
Accessories:  
**25-5835** Iron Black pier mount base



# ROXTON LED



## Large Wall Lantern

**62-812** Umber Bay / Frosted Seed Glass

(1) 15W LED Light Engine / Dimmable

Dimensions: Width 8½", Height 16½", Extension 8¾"

Lumens: 1,190\*, CCT: 3000K, CRI: 80



### Flush Lantern

**62-813** Umber Bay / Frosted Seed Glass  
(1) 15W LED Panel / Dimmable  
Dimensions: Width 11 3/4", Height 4 1/4"  
Lumens: 1,190\*, CCT: 3000K, CRI: 80



### Hanging Lantern

**62-814** Umber Bay / Frosted Seed Glass  
(1) 15W LED Light Engine / Dimmable  
Dimensions: Width 8 1/2", Height 16 1/2",  
Chain 48", Wire 12"  
Lumens: 1,190\*, CCT: 3000K, CRI: 80  
Accessories:  
**25-5654** 3' Section of matching chain



### Small Wall Lantern

**62-811** Umber Bay / Frosted Seed Glass  
(1) 12W LED Light Engine / Dimmable  
Dimensions: Width 6 1/2", Height 13 3/8", Extension 6 7/8"  
Lumens: 950\*, CCT: 3000K, CRI: 80



### Post Lantern

**62-815** Umber Bay / Frosted Seed Glass  
(1) 15W LED Light Engine / Dimmable  
Dimensions: Width 8 1/2", Height 19 1/2"  
Lumens: 1,190\*, CCT: 3000K, CRI: 80  
Accessories:  
**25-5815** Umber Bay pier mount base



# HOWELL



## Large Wall Lantern

**60-5833** Bronze with Copper Accents / Clear Seeded Glass

(1) 60W A19 max. / Medium Base

**S2423** 60W ST19 Vintage Lamp Included

Dimensions: Width 8<sup>3</sup>/<sub>4</sub>", Height 17<sup>1</sup>/<sub>8</sub>", Extension 8<sup>3</sup>/<sub>4</sub>"



### Flush Lantern

**60-5834** Bronze with Copper Accents / Clear Seeded Glass  
(2) 60W A19 max. / Medium Base  
**S2423** 60W ST19 Vintage Lamps Included  
Dimensions: Width 12", Height 4 1/8"



### Hanging Lantern

**60-5836** Bronze with Copper Accents / Clear Seeded Glass  
(1) 60W A19 max. / Medium Base  
**S2423** 60W ST19 Vintage Lamp Included  
Dimensions: Width 8 3/4", Height 17 1/8",  
Chain 48", Wire 12"  
Accessories:  
**25-4225** 3' Section of matching chain



### Small Wall Lantern

**60-5831** Bronze with Copper Accents / Clear Seeded Glass  
(1) 60W A19 max. / Medium Base  
**S2423** 60W ST19 Vintage Lamp Included  
Dimensions: Width 5 1/4", Height 11 1/8", Extension 5 3/8"



### Medium Wall Lantern

**60-5832** Bronze with Copper Accents / Clear Seeded Glass  
(1) 60W A19 max. / Medium Base  
**S2423** 60W ST19 Vintage Lamp Included  
Dimensions: Width 7", Height 14 1/8", Extension 7 1/8"



### Post Lantern

**60-5835** Bronze with Copper Accents / Clear Seeded Glass  
(1) 60W A19 max. / Medium Base  
**S2423** 60W ST19 Vintage Lamp Included  
Dimensions: Width 8 3/4", Height 19 3/8"  
Accessories:  
**25-5615** Bronze pier mount base



# LED TRACK HEADS



## Round

**TH401** White, 24° Beam

**TH403** White, 36° Beam

(1) 12W LED Module

Dimensions: Width 3", Height 2 1/4",  
Extension 5 1/8"

Lumens: 820\*, CCT: 3000K, CRI: 90



## Round

**TH402** Black, 24° Beam

**TH404** Black, 36° Beam

(1) 12W LED Module

Dimensions: Width 3", Height 2 1/4",  
Extension 5 1/8"

Lumens: 820\*, CCT: 3000K, CRI: 90





### Pinch Back

**TH411** White, 24° Beam

**TH413** White, 36° Beam

(1) 12W LED Module

Dimensions: Width 2<sup>3</sup>/<sub>4</sub>", Height 2<sup>3</sup>/<sub>4</sub>",  
Extension 5<sup>5</sup>/<sub>8</sub>"

Lumens: 820\*, CCT: 3000K, CRI: 90



### Angle Arm

**TH421** White, 24° Beam

**TH423** White, 36° Beam

(1) 12W LED Module

Dimensions: Width 2<sup>1</sup>/<sub>2</sub>", Height 2<sup>3</sup>/<sub>8</sub>",  
Extension 6<sup>1</sup>/<sub>4</sub>"

Lumens: 820\*, CCT: 3000K, CRI: 90



### Pinch Back

**TH412** Black, 24° Beam

**TH414** Black, 36° Beam

(1) 12W LED Module

Dimensions: Width 2<sup>3</sup>/<sub>4</sub>", Height 2<sup>3</sup>/<sub>4</sub>",  
Extension 5<sup>5</sup>/<sub>8</sub>"

Lumens: 820\*, CCT: 3000K, CRI: 90



### Angle Arm

**TH422** Black, 24° Beam

**TH424** Black, 36° Beam

(1) 12W LED Module

Dimensions: Width 2<sup>1</sup>/<sub>2</sub>", Height 2<sup>3</sup>/<sub>8</sub>",  
Extension 6<sup>1</sup>/<sub>4</sub>"

Lumens: 820\*, CCT: 3000K, CRI: 90

# TWIST AND LOCK 120-277V LED



## 12" Flush 120-277V

**62-786\*\*** Brushed Nickel / Frosted Glass  
(1) 18W LED Module  
Dimensions: Width 11 3/4", Height 4 1/2"  
Lumens: 1,080\*, CCT: 3000K, CRI: 90



## 14" Flush 120-277V

**62-788\*\*** Brushed Nickel / Frosted Glass  
(1) 24W LED Module  
Dimensions: Width 14", Height 5 1/2"  
Lumens: 1,440\*, CCT: 3000K, CRI: 90



### 12" Flush 120-277V

**62-787\*\*** Mahogany Bronze / Frosted Glass  
(1) 18W LED Module  
Dimensions: Width 11 3/4", Height 4 1/2"  
Lumens: 1,080\*, CCT: 3000K, CRI: 90



### 14" Flush 120-277V

**62-789\*\*** Mahogany Bronze / Frosted Glass  
(1) 24W LED Module  
Dimensions: Width 14", Height 5 1/2"  
Lumens: 1,440\*, CCT: 3000K, CRI: 90

twist and lock LED

# PUFF LED

AVAILABLE WITH  
OCCUPANCY SENSOR



LED module



LED module with occupancy sensor  
(functions through the outer lens)



Item#	Description	Finish	Cover	Watts	Light Source	cETLus	CCT	Lumens	CRI	Hours	Width	Height
62-545**	11" LED flush	White	Acrylic	12.5	LED Module	Damp	3000K	900*	>80	50,000	11"	3 1/8"
62-546	11" LED flush w/occupancy sensor	White	Acrylic	13.5	LED Module	Damp	3000K	900*	>80	50,000	11"	3 1/8"
62-547**	14" LED flush	White	Acrylic	16.5	LED Module	Damp	3000K	1,200*	>80	50,000	14"	3 1/2"
62-548	14" LED flush w/occupancy sensor	White	Acrylic	17.5	LED Module	Damp	3000K	1,200*	>80	50,000	14"	3 1/2"

# PUFF 120-277V LED

AVAILABLE WITH OCCUPANCY  
SENSOR OR VACANCY SENSOR



LED module



LED module with occupancy sensor or 50% dimming  
vacancy sensor (functions through the outer lens)

puff LED



Item#	Description	Finish	Cover	Watts	Light Source	cETLus	CCT	Lumens	CRI	Hours	Width	Height
62-795**	11" LED flush	White	Acrylic	12.5	LED Module	Damp	3000K	875*	>90	40,000	11 5/8"	3 1/8"
62-796**	14" LED flush	White	Acrylic	16.5	LED Module	Damp	3000K	1,170*	>90	40,000	14"	3 1/2"
62-797	14" LED flush w/occupancy sensor	White	Acrylic	17.5	LED Module	Damp	3000K	970*	>90	40,000	14"	3 1/2"
62-798	14" LED flush w/vacancy sensor	White	Acrylic	17.5	LED Module	Damp	3000K	970*	>90	40,000	14"	3 1/2"

\*Lumens measured at LED source. \*\*Dimmable (at 120V only). cETLus damp location.

# PUFF 120-277V LED

0-10V DIMMING



LED module



Item#	Description	Finish	Cover	Watts	Light Source	cETLus	CCT	Lumens	CRI	Hours	Width	Height
62-791	11" LED flush 0-10V dimming	White	Acrylic	12.5	LED Module	Damp	3000K	875*	>90	50,000	11 5/8"	3 1/8"
62-792	14" LED flush 0-10V dimming	White	Acrylic	16.5	LED Module	Damp	3000K	1,170*	>90	50,000	14"	3 1/2"

# PUFF 120-277V LED

BATTERY BACK-UP  
READY



Battery back-up ready (EMR). Indicator light and test button on battery back-up module shown (not included).



LED module



Emergency battery back-up module (not included)  
S9299 120V Battery back-up disk  
S9780 277V Battery back-up disk

puff LED



Item#	Description	Finish	Cover	Watts	Light Source	cETLus	CCT	Lumens	CRI	Hours	Width	Height
62-991**	11" LED flush emergency battery back-up ready (battery back-up module not included)	White	Acrylic	16.5	LED Module	Damp	3000K	960*	>90	40,000	14"	4 3/4"
S9299	120V Battery back-up disk											
S9780	277V Battery back-up disk											

\*Lumens measured at LED source. \*\*Dimmable (at 120V only). cETLus damp location.

# MUSHROOM LED



## Installation Options

Option 1



Simple to install. Just screw it on!

Option 2



Also installs easily into a junction box.



Integrated circular LED module for consistency and dependability.



Item#	Description	Finish	Cover	Watts	Light Source	cETLus	CCT	Lumens	CRI	Hours	Width.	Height
62-961**	7" LED Mushroom	White	Acrylic	13.5	LED Module	Damp	2700K	800*	>90	50,000	7 5/8"	3 3/4"
62-962**	7" LED Mushroom	White	Acrylic	13.5	LED Module	Damp	3000K	820*	>90	50,000	7 5/8"	3 3/4"
62-963**	7" LED Mushroom	White	Acrylic	13.5	LED Module	Damp	4000K	860*	>90	50,000	7 5/8"	3 3/4"
62-964**	7" LED Mushroom	White	Acrylic	13.5	LED Module	Damp	5000K	1,050*	>90	50,000	7 5/8"	3 3/4"



# MUSHROOM LED WITH PULL CHAIN



mushroom LED

## Installation Options

Option 1



Simple to install.  
Just screw it on!

Option 2



Also installs easily  
into a junction box.



Integrated circular  
LED module for  
consistency and  
dependability.



Item#	Description	Finish	Cover	Watts	Light Source	cETLus	CCT	Lumens	CRI	Hours	Width.	Height
62-965**	7" LED Mushroom w/ pull chain	White	Acrylic	13.5	LED Module	Damp	3000K	820*	>90	50,000	7 5/8"	3 3/4"
62-966**	7" LED Mushroom w/ pull chain	White	Acrylic	13.5	LED Module	Damp	4000K	860*	>90	50,000	7 5/8"	3 3/4"

\*Lumens measured at LED source. \*\*Dimmable. cETLus damp location.

# INDEX

60-5081 . . . . .	7	60-5838 . . . . .	46	60-5931 . . . . .	13
60-5082 . . . . .	6	60-5839 . . . . .	46	60-5937 . . . . .	13
60-5083 . . . . .	7	60-5841 . . . . .	16	60-5942 . . . . .	13
60-5084 . . . . .	7	60-5842 . . . . .	17	60-5948 . . . . .	13
60-5091 . . . . .	5	60-5843 . . . . .	17	60-5961 . . . . .	12
60-5092 . . . . .	4	60-5844 . . . . .	17	60-5964 . . . . .	12
60-5093 . . . . .	5	60-5847 . . . . .	47	60-5967 . . . . .	12
60-5094 . . . . .	5	60-5848 . . . . .	47	60-6121 . . . . .	29
60-5761 . . . . .	18	60-5849 . . . . .	47	60-6122 . . . . .	29
60-5762 . . . . .	20	60-5851 . . . . .	37	60-6123 . . . . .	29
60-5763 . . . . .	21	60-5852 . . . . .	37	60-6124 . . . . .	28
60-5764 . . . . .	21	60-5853 . . . . .	37	60-6125 . . . . .	27
60-5765 . . . . .	19	60-5854 . . . . .	36	60-6126 . . . . .	27
60-5766 . . . . .	21	60-5855 . . . . .	37	60-6127 . . . . .	27
60-5767 . . . . .	21	60-5856 . . . . .	35	60-6128 . . . . .	26
60-5771 . . . . .	22	60-5857 . . . . .	35	60-6129 . . . . .	29
60-5772 . . . . .	24	60-5858 . . . . .	34	60-6131 . . . . .	31
60-5773 . . . . .	25	60-5859 . . . . .	35	60-6132 . . . . .	31
60-5774 . . . . .	25	60-5860 . . . . .	35	60-6133 . . . . .	30
60-5775 . . . . .	23	60-5861 . . . . .	44	60-6134 . . . . .	31
60-5776 . . . . .	25	60-5862 . . . . .	44	60-6135 . . . . .	31
60-5777 . . . . .	25	60-5866 . . . . .	45	62-545 . . . . .	100
60-5781 . . . . .	38	60-5867 . . . . .	45	62-546 . . . . .	100
60-5782 . . . . .	39	60-5881 . . . . .	8	62-547 . . . . .	100
60-5783 . . . . .	39	60-5882 . . . . .	9	62-548 . . . . .	100
60-5784 . . . . .	39	60-5883 . . . . .	9	62-786 . . . . .	98
60-5786 . . . . .	40	60-5884 . . . . .	9	62-787 . . . . .	99
60-5787 . . . . .	41	60-5885 . . . . .	9	62-788 . . . . .	98
60-5788 . . . . .	41	60-5886 . . . . .	10	62-789 . . . . .	99
60-5789 . . . . .	41	60-5887 . . . . .	11	62-791 . . . . .	102
60-5791 . . . . .	43	60-5888 . . . . .	11	62-792 . . . . .	102
60-5792 . . . . .	43	60-5889 . . . . .	11	62-795 . . . . .	101
60-5793 . . . . .	43	60-5890 . . . . .	11	62-796 . . . . .	101
60-5794 . . . . .	43	60-5891 . . . . .	33	62-797 . . . . .	101
60-5795 . . . . .	42	60-5892 . . . . .	33	62-798 . . . . .	101
60-5831 . . . . .	95	60-5893 . . . . .	33	62-801 . . . . .	55
60-5832 . . . . .	95	60-5894 . . . . .	33	62-802 . . . . .	55
60-5833 . . . . .	94	60-5895 . . . . .	32	62-803 . . . . .	55
60-5834 . . . . .	95	60-5896 . . . . .	14	62-804 . . . . .	54
60-5835 . . . . .	95	60-5897 . . . . .	15	62-805 . . . . .	53
60-5836 . . . . .	95	60-5898 . . . . .	15	62-806 . . . . .	53
60-5837 . . . . .	46	60-5899 . . . . .	15	62-807 . . . . .	54

62-808.....	55	62-882.....	66	62-944.....	87
62-809.....	55	62-886.....	67	62-945.....	87
62-810.....	52	62-887.....	67	62-946.....	87
62-811.....	93	62-888.....	71	62-951.....	73
62-812.....	92	62-891.....	51	62-952.....	73
62-813.....	93	62-892.....	51	62-953.....	72
62-814.....	93	62-893.....	50	62-954.....	72
62-815.....	93	62-894.....	50	62-955.....	73
62-821.....	89	62-895.....	51	62-961.....	104
62-822.....	88	62-896.....	51	62-962.....	104
62-823.....	89	62-897.....	51	62-963.....	104
62-824.....	89	62-901.....	59	62-964.....	104
62-825.....	89	62-902.....	59	62-965.....	105
62-831.....	91	62-903.....	59	62-966.....	105
62-832.....	90	62-904.....	58	62-985.....	77
62-833.....	91	62-905.....	57	62-986.....	77
62-834.....	91	62-906.....	57	62-987.....	76
62-835.....	91	62-907.....	58	62-988.....	77
62-837.....	68	62-908.....	59	62-989.....	76
62-838.....	69	62-909.....	59	62-990.....	77
62-841.....	60	62-910.....	56	62-991.....	103
62-842.....	60	62-911.....	80	62-992.....	74
62-846.....	61	62-912.....	80	62-993.....	74
62-847.....	61	62-913.....	81	62-994.....	74
62-851.....	62	62-914.....	81	62-995.....	75
62-852.....	62	62-915.....	80	62-996.....	75
62-856.....	63	62-916.....	81	62-997.....	75
62-857.....	63	62-921.....	82	S9299.....	103
62-861.....	64	62-922.....	82	S9780.....	103
62-862.....	64	62-923.....	83	TH401.....	96
62-866.....	65	62-924.....	83	TH402.....	96
62-867.....	65	62-925.....	82	TH403.....	96
62-871.....	78	62-926.....	83	TH404.....	96
62-872.....	78	62-931.....	84	TH411.....	97
62-873.....	79	62-932.....	84	TH412.....	97
62-874.....	79	62-933.....	85	TH413.....	97
62-875.....	78	62-934.....	85	TH414.....	97
62-876.....	79	62-935.....	84	TH421.....	97
62-877.....	70	62-936.....	85	TH422.....	97
62-878.....	70	62-941.....	87	TH423.....	97
62-879.....	71	62-942.....	87	TH424.....	97
62-881.....	66	62-943.....	86		



index



www.nuvolighting.com  
Catalog NU1270  
\$10.00



National Toll-Free: **1.800.43.SATCO** (1.800.437.2826) [www.satco.com](http://www.satco.com)

Corporate Offices & Distribution Center: **NEW YORK** 110 Heartland Blvd., Brentwood, NY 11717 800.437.2826 631.243.2022 Fax 631.243.2027

Distribution Centers: **FLORIDA** 900 N.W. 159th Drive, Miami, FL 33169 800.437.2826 305.624.2044 FAX 305.623.0286  
**CALIFORNIA** 31288 San Benito St. Hayward, CA 94544 800.437.2826 510.487.4822 FAX 510.487.8955  
**WASHINGTON** 4710 116th St. S.W., Mukilteo, WA 98275 800.437.2826 425.789.3300 FAX 425.789.3310  
**TEXAS** 2000 Valwood Parkway, Farmers Branch, TX 75234 800.437.2826 972.247.2437 FAX 972.247.5408  
**PUERTO RICO** Campeche St. 23, Julio N. Matos Industrial Park, Carolina, PR 00984 787.757.3510 FAX 787.757.3540



Like us!



Follow us!

© Copyright 2016, SATCO Products, Inc