



MOMENT Kim's outdoor living area provides a quiet and comfortable respite from her busy career. The *Moment* when you welcome a new season in life.

Kim P., Customer Service

Outdoor & Landscape



OUTDOOR LIGHTING ENHANCES THE BEAUTY OF YOUR PROPERTY WHILE PROVIDING SAFETY AND SECURITY.

Outdoor lighting also allows you to take advantage of your outdoor spaces after dark, while adding value to your home. Landscape lighting can make a property shine in more ways than one. With proper planning, lighting can help create a usable and safe outdoor space, and also complement a home's exterior.

STYLE BOARD

RUSTIC FARMHOUSE

Clean and simple with a country flair, this style's characteristics include rich wood tones, rustic antique decor, a white color palette and an open floor plan.

THE LOOK

FURNISHINGS
Simplicity



This style represents the simplicity and common sense functionality of country living while incorporating an antique charm to any lifestyle.

COLOR PALETTE
Clean White



Stick to a white color palette throughout the home and accent with organic items and plants. This creates a clean, simple look.

MATERIALS
Rich Wood Tones



Designers love to find weathered, antique-style decor to flatter this country feel. Spruce up the design with fun accessories.

THE COLORS



THE LIGHTS

SPOT THE TREND RUSTIC ANTIQUE LIGHTING

Fixture finishes like Antique Bronze add to the Rustic Farmhouse style. Designers often use fixtures with rich wood tones, such as Turnbury, to complete a room.



TURNBURY
P4761-141



ASPEN CREEK
P50020-009



DEBUT
P400015-009



STAUTON
P5333-09 (cluster)



LIGHTING DESIGN TIP ✦

Outdoor lanterns can work to preserve an older home's overall character, while providing a refreshing update. This bungalow boasts new Cadence outdoor fixtures, yet is able to maintain the charming style that defines the neighborhood.

DESIGN FEATURE



LIGHTING DESIGN TIP ✦

As more homeowners view their exterior areas as a key location for entertainment and relaxation, the design, functionality and efficiency of outdoor lighting has taken center stage. Consider all perspectives when tackling a lighting design plan to extend the outdoor living season.



Featuring Aluminum Squares and LED Recessed

OUTDOOR LED SOLUTIONS



I encounter people who are confused by all the LED options out there. Or, maybe they've had a bad experience from an LED product in the past. Don't be afraid to ask an expert if you're intimidated by lighting technology."



KELLY INGLIS
Designer/Wolseley Studio

Featuring Aluminum Squares and Haven



Featuring LED step lights and LED recessed lights
(Image: Kelly Inglis)

LIGHTING TECHNIQUES / WHY CHOOSE OUTDOOR LED?

THEY'RE SAFE

LEDs don't produce an exceptional amount of heat like other landscape and outdoor options.

THEY SAVE ENERGY

Because outdoor lights are often left on for hours at a time, energy saving benefits are even more applicable to outdoor settings.

THEY'RE LOW MAINTENANCE

An LED lamp can last up to 20 years!

BENEFITS OF A WELL-LIT EXTERIOR

SECURITY // Increasing light levels to allow visibility in both lit and unlit areas can deter intruders.

SAFETY // Properly lit walkways and stairs helps to prevent falls.

USABILITY // You can extend the outdoor living season and enjoy decks and patio areas with a well lit environment.

AESTHETICS // Consider the visual experience of guests and light focal points to bring out the beauty of the property.

OUTDOOR LED FOUR WAYS

1 WALL LANTERNS

Like down lights, LED wall lanterns contribute to the mood of outdoor living areas. Make guests feel at ease in your outdoor space by positioning wall lanterns around popular gathering spaces.



P6057-3130K9

2 DOWN LIGHTS

Shine LED down lights on areas ideal for outdoor entertaining. Recessed LED fixtures create a comfortable environment and add to your home's safety and security.



P8071-09-30K

3 SPOTLIGHTS

LED spotlights can be used to highlight architecture, gardens and key focal points of your landscape design. Spotlights also add visual intrigue to exterior areas, boosting curb appeal.



P5299-31

4 PATH LIGHTS

Guide guests along exterior pathways and steps using LED path lights.



P5246-31

CONTENTS

Address Lights	732	Fairview	685	Penfield	674
Alum Cylinders	726	Format	689	Pier 33	690
Andover	658	Gibbes	652	Poles	734
Anson	693	Globes	719	Poly	720
Archives	648	Greetings	686	Prairie	682
Arrive	669	Hard Knox	722	Preswick	644
Arts & Crafts	684	Hard Knox CFL	723	Refuge	646
Ashmore	638	Hawthorne	680	Residence	673
Bay Court	687	Jack	692	Resort	640
Bell LED	697	Kiawah	654	Roman Coach	708
Beveled Cast	715	Landscape Access.	748	Roman Coach CFL	710
Botta	648	LED Cylinders	724	Santee	653
BrassGuard	712	LED Landscape	738	Security	731
Brookside	656	LED Z-1010	691	Shelton	723
Bulkheads	718	LED Z-2020	691	Signal Bay	647
Burlington	706	MAC	678	Square cylinder	728
Cadence	628	Maison	630	Street	653
Coach lanterns	714	Mansard	717	Tork Night Saver	733
Compel	688	Meadowlark	642	Township	651
Cornice	696	Meridian	635	Transformers	748
Coventry	660	Merit	679	Twain	668
Crawford	632	Milford	711	Union Square	650
Creighton	649	New Haven	707	Utility Ceiling	715
Deck & Step Lights	746	Newport	716	Valera	694
Derby	670	Non Metallic	721	Verdae	637
Devereux	634	CFL & LED		Welbourne	664
Dibbs	667	Non Metallic	717	Well Lights	744
District	698	Lanterns		Westport	702
Door Chime	733	Nottingham	636	Westport CFL LED	704
East Haven	700	Onion	662	Wish	676
Edition	666	Pagoda	743		
Ellipses	690	Par	730		
Enchant	643	Parker	693		
Endicott	672	Path Lights	740		
Endorse	655	Pedigree	663		
Essential	683	Peek-a-Boo	692		



MOMENT Virginia enjoys catching up with her neighbors who pass by their patio, while giving her dog, Buddy, some well-deserved attention. The Moment when you find unconditional love.

Virginia S., Sales



CADENCE GU24



Clear seeded water glass panes with etched pillar diffuser uses energy efficient compact fluorescent or LED lamps.

FINISH

- Black - 31

POST LANTERN

P6439-31 Black
10" dia., 23" ht.
Fits 3" post (order separately).
One GU24 lamp,
26w max.



HANGING LANTERN

P6539-31 Black
10" dia., 24-5/8" ht.
Overall ht. w/chain 100", wire 10'.
One GU24 lamp,
26w max.



SMALL WALL LANTERN

P6626-31 Black
6-1/8" W., 18-7/8" ht.
Extends 7-1/2". H/CTR 9-1/4".
One GU24 lamp,
18w max.



MEDIUM WALL LANTERN

P6627-31 Black
8" W., 24-3/4" ht.
Extends 9-1/4". H/CTR 13-3/8".
One GU24 lamp,
26w max.



LARGE WALL LANTERN

P6628-31 Black
10" W., 31" ht.
Extends 11-3/8". H/CTR 14-1/8".
One GU24 lamp,
26w max.



EXTRA-LARGE WALL LANTERN

P6629-31 Black
12" W., 38" ht.
Extends 13-1/4". H/CTR 18-1/4".
One GU24 lamp,
26w max.



P6626-31



P6539-31



P6628-31




P6627-31



P6629-31



P6439-31



The Cadence lantern collection showcases classic styling. Clear water glass panels showcase traditional lighting clusters. Mediterranean-style frame is finished in Oil Rubbed Bronze.

FINISH

- Oil Rubbed Bronze - 108



SMALL WALL-LANTERN

P6080-108 Oil Rubbed Bronze
 6" W., 16-1/4" ht.
 Extends 7-1/4". H/CTR 7-3/4".
 One medium base lamp,
 100w max.

LARGE WALL LANTERN

P6639-108 Oil Rubbed Bronze
 10" W., 26-5/8" ht.
 Extends 11-1/2". H/CTR 9-5/8".
 Three candelabra base lamps,
 each 60w max.

POST LANTERN

P6442-108 Oil Rubbed Bronze
 10" sq., 22-5/8" ht.
 Fits 3" post (order separately).
 Three candelabra base lamps,
 each 60w max.

EXTRA-LARGE WALL LANTERN

P6640-108 Oil Rubbed Bronze
 12-1/4" W., 32" ht.
 Extends 13-3/4". H/CTR 11-5/8".
 Four candelabra base lamps,
 each 60w max.



HANGING LANTERN

P6542-108 Oil Rubbed Bronze
 10" sq., 24" ht.
 Overall ht. w/chain 99-1/2"; wire 15'.
 Three candelabra base lamps,
 each 60w max.

MEDIUM WALL LANTERN

P6638-108 Oil Rubbed Bronze
 8" W., 21-1/4" ht.
 Extends 9-3/8". H/CTR 9-7/8".
 Two candelabra base lamps,
 each 60w max.

MAISON GU24



Maison offers French country styling for a variety of home settings. Classic and formal clear water seeded glass in a die-cast aluminum frame. GU24 version with etched pillar diffuser.

FINISH

- Black - 31

POST LANTERN

P6441-31 Black
10-1/2" dia., 26-3/8" ht.
Fits 3" post (order separately).
One GU24 lamp,
26w max.

**LARGE WALL LANTERN**

P6636-31 Black
8-1/2" W., 19-3/4" ht.
Extends 8-7/8". H/CTR 13-3/8".
One GU24 lamp,
26w max.

**HANGING LANTERN**

P6541-31 Black
10-1/2" dia., 24-1/2" ht. Overall ht.
w/chain 100-1/2", wire 10'.
One GU24 lamp,
26w max.

**EXTRA-LARGE WALL LANTERN**

P6637-31 Black
10-1/2" W., 23-3/4" ht.
Extends 11-1/4". H/CTR 16-3/8".
One GU24 lamp,
26w max.

**SMALL WALL LANTERN**

P6634-31 Black
5-3/4" W., 13-5/8" ht.
Extends 6-1/8". H/CTR 9-1/8".
One GU24 lamp,
18w max.

**MEDIUM WALL LANTERN**

P6635-31 Black
7-1/4" W., 16-7/8" ht.
Extends 7-7/8". H/CTR 11-3/4".
One GU24 lamp,
26w max.



P6634-31



P6541-31



P6636-31



P6635-31



P6637-31



P6441-31



FINISHES

- Black - 31
- Oil Rubbed Bronze - 108

SMALL WALL LANTERN

P5753-31 Black
P5753-108 Oil Rubbed Bronze
 5-3/4" W., 16-1/4" ht.
 Extends 8-5/8". H/CTR 9".
 One medium base lamp,
 100w max.

MEDIUM WALL LANTERN

P5754-31 Black
P5754-108 Oil Rubbed Bronze
 7-1/4" W., 20" ht.
 Extends 10-1/2". H/CTR 10-5/8".
 Two candelabra base lamps,
 each 60w max.

LARGE WALL LANTERN

P5755-31 Black
P5755-108 Oil Rubbed Bronze
 8-1/2" W., 23-3/4" ht.
 Extends 12". H/CTR 13-1/2".
 Three candelabra base lamps,
 each 60w max.

POST LANTERN

P6432-31 Black
P6432-108 Oil Rubbed Bronze
 7-1/4" dia., 20-5/8" ht.
 Fits 3" post (order separately).
 Two candelabra base lamps,
 each 60w max.

HANGING LANTERN

P6532-31 Black
P6532-108 Oil Rubbed Bronze
 7-1/4" dia., 17-7/8" ht.
 Overall ht. w/chain 93"; wire 10'.
 Two candelabra base lamps,
 each 60w max.

DESIGN+SERIES
CRAWFORD GU24




Transform the outdoors with timeless styling. Die-cast aluminum with etched flat glass. Energy efficient. Powder coat finish. Hinged door for easy relamping.*


FINISHES

- Black - 31
- Oil Rubbed Bronze - 108


MEDIUM WALL LANTERN

P5686-31 Black
P5686-108 Oil Rubbed Bronze
 8-1/2" W., 16-3/4" ht.
 Extends 11-1/8" H/CTR 9-5/8".
 One GU24 CFL lamp,
 26w max. 


POST LANTERN

P6440-31 Black
 9-7/8" W., 24-5/8" ht.
 Fits 3" post (order separately).
 One GU24 CFL lamp,
 26w max. 


HANGING LANTERN*

P6540-31 Black
 9-7/8" dia., 26-5/8" ht.
 Overall ht. w/ chain 102"; wire 10'.
 One GU24 CFL lamp,
 26w max. 


SMALL WALL LANTERN*

P6630-31 Black
 6-1/2" W., 1-1/2" ht.
 Extends 8-3/4". H/CTR 8".
 One GU24 CFL lamp,
 26w max. 


MEDIUM WALL LANTERN*

P6631-31 Black
 8-1/2" W., 20-1/2" ht.
 Extends 11".
 H/CTR 8-3/8".
 One GU24 CFL lamp,
 26w max. 

LARGE WALL LANTERN*

P6632-31 Black
 9-7/8" W., 28-7/8" ht.
 Extends 12-5/8". H/CTR 8-3/8".
 One GU24 CFL lamp,
 26w max. 

EXTRA-LARGE WALL LANTERN

P6633-31 Black
 12" W., 32-7/8" ht.
 Extends 14-3/4". H/CTR 14-7/8".
 One GU24 CFL lamp,
 26w max. 



P6630-31



P5686-108



P5686-31



P6632-31



P6440-31



P6633-31



P6631-31



P5670-108



P5671-108



P5474-108



P5574-108



P5672-108



P5673-108



Cast lanterns with clear beveled glass and Oil Rubbed Bronze finish in a die-cast aluminum frame. Hinged door for easy relamping.*

FINISH

● Oil Rubbed Bronze - 108

POST LANTERN*

P5474-108 Oil Rubbed Bronze
12" dia., 28-1/2" ht.
Fits 3" post (order separately).
Four candelabra base lamps,
each 60w max.

LARGE WALL LANTERN*

P5672-108 Oil Rubbed Bronze
10" W., 29" ht.
Extends 12-1/2". H/CTR 11-5/8".
Three candelabra base lamps,
each 60w max.

HANGING LANTERN*

P5574-108 Oil Rubbed Bronze
12" dia., 29-3/8" ht.
Overall ht. w/ chain 68"; wire 15'.
Four candelabra base lamps,
each 60w max.

EXTRA-LARGE WALL LANTERN*

P5673-108 Oil Rubbed Bronze
12" W., 32-3/4" ht.
Extends 14-3/4". H/CTR 14-3/4".
Four candelabra base lamps,
each 60w max.


SMALL WALL LANTERN

P5670-108 Oil Rubbed Bronze
6-1/2" W., 12-1/2" ht.
Extends 8-3/4". H/CTR 8".
One medium base lamp,
100w max.

MEDIUM WALL LANTERN*

P5671-108 Oil Rubbed Bronze
8-1/2" W., 16-3/4" ht.
Extends 11-1/8" H/CTR 9-5/8".
Two candelabra base lamps,
each 60w max.

DESIGN+SERIES
DEVEREUX



Devereux features an etched white pillar shade that sits inside a clear seeded glass design. A double scrolled arm finished in Antique Bronze provides elegant scale for a variety of exterior settings. Post, hanging and wall lantern options are available.

FINISH

- Antique Bronze - 020

POST LANTERN

P540003-020 Antique Bronze
9-3/8" dia., 26-5/8" ht.
Fits 3" post (order separately).
One medium base lamp,
100w max.

HANGING LANTERN

P550003-020 Antique Bronze
9-1/2" dia., 23-5/8" ht.
Overall ht. w/chain 95-1/2"; wire 10'.
One medium base lamp,
100w max.

SMALL WALL-LANTERN

P560018-020 Antique Bronze
5-1/2" W., 20-1/4" ht.
Extends 7-7/8". H/CTR 10-1/8".
One medium base lamp,
100w max.

MEDIUM WALL-LANTERN

P560019-020 Antique Bronze
7" W., 26" ht.
Extends 9-3/4". H/CTR 13".
One medium base lamp,
100w max.

LARGE WALL-LANTERN

P560020-020 Antique Bronze
9-1/2" W., 34-1/2" ht.
Extends 12-3/4". H/CTR 17-3/8".
One medium base lamp,
100w max.

P560018-020



P560019-020



P560020-020



P550003-020



P540003-020





Decorative shepherd hooks and acanthus leaf cast arms. Clear seeded glass urns in a die-cast aluminum Black frame.

FINISH

- Black - 31

POST LANTERN

P5420-31 Black
12" dia., 26" ht. Fits 3" post (order separately).
Three candelabra base lamps, each 60w max.

MEDIUM WALL LANTERN

P5823-31 Black
9" W., 19-3/4" ht.
Extends 12-1/2". H/CTR 10".
Two candelabra base lamps, each 60w max.

HANGING LANTERN

P5520-31 Black
12" dia., 24-1/4" ht.
Overall ht. w/chain 99"; wire 15'
Three candelabra base lamps, each 60w max.

LARGE WALL LANTERN

P5824-31 Black
12" W., 27" ht.
Extends 16-1/2". H/CTR 8-1/4".
Three candelabra base lamps, each 60w max.

SMALL WALL LANTERN

P5820-31 Black
6-3/4" W., 15" ht.
Extends 9-5/8". H/CTR 5-1/2".
One medium base lamp, 100w max.

MEDIUM WALL LANTERN

P5822-31 Black
9" W., 20-1/4" ht.
Extends 12-1/2". H/CTR 7-1/2".
Two candelabra base lamps, each 60w max.

NOTTINGTON

Scrolling cast arms, fluted bodies and acorn accents. Clear seeded glass with Gilded Iron or Forged Bronze powder coat finish. Cast aluminum construction.

FINISHES

- Gilded Iron - 71
- Forged Bronze - 77

POST LANTERN

P5438-71 Gilded Iron

P5438-77 Forged Bronze

10" dia., 22-1/2" ht.

Fits 3" post (order separately).

Three candelabra base lamps, each 60w max.

P5836-77



P5836-71



P5538-71



HANGING LANTERN

P5538-71 Gilded Iron

P5538-77 Forged Bronze

10" dia., 23-3/4" ht.

Overall ht. w/chain 63"; wire 15'

Three candelabra base lamps, each 60w max.

MEDIUM WALL LANTERN

P5835-71 Gilded Iron

P5835-77 Forged Bronze

8" W., 19-5/8" ht.

Extends 10-5/8". H/CTR 10-5/8".

Two candelabra base lamps, each 60w max.

P5837-77



P5837-71



P5835-77



MEDIUM WALL LANTERN

P5836-71 Gilded Iron

P5836-77 Forged Bronze

8" W., 19-5/8" ht.

Extends 10-5/8". H/CTR 8".

Two candelabra base lamps, each 60w max.

LARGE WALL LANTERN

P5837-71 Gilded Iron

P5837-77 Forged Bronze

10" W., 26" ht.

Extends 13". H/CTR 9-1/2".

Three candelabra base lamps, each 60w max.

P5838-77



P5838-71



P5438-77



DESIGN+SERIES
VERDAE

Classic and formal clear seeded glass complements a Black or Antique Bronze finish. Open bottom or hinged door provide easy access for cleaning and relamping.

FINISHES

- Antique Bronze - 020
- Black - 031

POST LANTERN

P540002-020 Antique Bronze
P540002-031 Black
10-3/8" dia., 22-5/8" ht.
Fits 3" post (order separately).
Three candelabra base lamps,
each 60w max.

LARGE WALL-LANTERN

P560016-020 Antique Bronze
P560016-031 Black
10-3/8" W., 21-3/4" ht.
Extends 13-5/8". H/CTR 10".
Three candelabra base lamps,
each 60w max.

HANGING LANTERN

P550002-020 Antique Bronze
P550002-031 Black
10-3/8" dia., 18-3/8" ht.
Overall ht. w/chain 93-1/2"; wire 10'.
Three candelabra base lamps,
each 60w max.

EXTRA-LARGE WALL-LANTERN

P560017-020 Antique Bronze
P560017-031 Black
10-3/8" W., 30-1/2" ht.
Extends 13-1/4". H/CTR 14-3/4".
Three candelabra base lamps,
each 60w max.

SMALL WALL-LANTERN

P560014-020 Antique Bronze
P560014-031 Black
6-1/4" W., 13-1/4" ht.
Extends 8-5/8". H/CTR 5-3/4".
One medium base lamp,
100w max.

MEDIUM WALL-LANTERN

P560015-020 Antique Bronze
P560015-031 Black
8-1/4" W., 17-3/4" ht.
Extends 11-3/8". H/CTR 10-1/8".
One medium base lamp,
100w max.



P550002-020



P550002-031



P560014-020



P560014-031



P560015-020



P560015-031



P560016-020



P560016-031



P560017-020



P560017-031



P540002-020



P540002-031

ASHMORE

Handsome details, quill-scrolled arms and decorative finials. Textured Black or Antique Bronze finish. Die-cast aluminum construction with water seeded glass.

FINISHES

- Antique Bronze - 20
- Textured Black - 31

PAIR WITH

Path Light, page 740

POST LANTERN

P5450-20 Antique Bronze

P5450-31 Textured Black

9-5/8" dia., 23-3/4" ht.

Fits 3" post (order separately).

Three candelabra base lamps, each 60w max.

HANGING LANTERN

P5550-20 Antique Bronze

P5550-31 Textured Black

9-5/8" dia., 17-3/4" ht.

Overall ht. w/ chain 92"; wire 10'.

Three candelabra base lamps, each 60w max.

FLUSH MOUNT

P5562-20 Antique Bronze

P5562-31 Textured Black

10-1/2" dia., 9-3/4" ht.

Two candelabra base lamps, each 60w max.

SMALL WALL LANTERN

P5649-20 Antique Bronze

P5649-31 Textured Black

6-5/8" dia., 14-7/8" ht.

Extends 9-3/8". H/CTR 4-1/2".

Two candelabra base lamps, each 60w max.

MEDIUM WALL LANTERN

P5650-20 Antique Bronze

P5650-31 Textured Black

8-5/8" dia., 16-1/2" ht.

Extends 10-3/8". H/CTR 4-1/2".

Three candelabra base lamps, each 60w max.

LARGE WALL LANTERN

P5651-20 Antique Bronze

P5651-31 Textured Black

9-5/8" dia., 20-1/2" ht.

Extends 12-3/4". H/CTR 7".

Three candelabra base lamps, each 60w max.

LARGE WALL LANTERN

P5652-20 Antique Bronze

P5652-31 Textured Black

8-5/8" dia., 26-1/2" ht.

Extends 12-3/8". H/CTR 19-1/8".

Three candelabra base lamps, each 60w max.

LARGE WALL LANTERN

P5653-20 Antique Bronze

P5653-31 Textured Black

9-5/8" dia., 27-1/2" ht.

Extends 12-3/4". H/CTR 20-1/2".

Three candelabra base lamps, each 60w max.

SMALL WALL LANTERN

P5854-20 Antique Bronze

P5854-31 Textured Black

Motion sensor wall lantern.

6-5/8" W., 15" ht.

Extends 9-5/8". H/CTR 10-1/4".

Two candelabra base lamps, each 60w max.

MEDIUM WALL LANTERN

P5875-20WB Antique Bronze

P5875-31WB Textured Black

Etched glass.

8-3/8" W., 16-5/8" ht.

Extends 10-1/2". H/CTR 4-1/2".

One GU24 CFL lamp, 26w max. included.



P5854-20



P5854-31



P5652-20



P5652-31



P5653-20



P5653-31



RESORT

Tudor styling meets Prairie design. Gradual ombré umber tint on glass shades. A woven cast pattern encases a casual profile. Large-scale cast aluminum lanterns feature powder coat finish in a warm Aged Copper finish.

FINISH

● Aged Copper - 122

SMALL WALL LANTERN

P5987-122 Aged Copper
6-1/2" W., 10-7/8" ht.
Extends 7-1/2". H/CTR 3-1/2".
One medium base lamp,
100w max.

MEDIUM WALL LANTERN

P5988-122 Aged Copper
8-1/2" W., 15-7/8" ht.
Extends 11-1/4". H/CTR 4-3/4".
One medium base lamp,
100w max.

LARGE WALL LANTERN

P5989-122 Aged Copper
10-1/2" W., 19-3/4" ht.
Extends 14". H/CTR 5-7/8".
One medium base lamp,
100w max.

POST LANTERN

P6404-122 Aged Copper
Decorative bottom grill.
8-1/2" dia., 17-3/8" ht. Fits 3"
post (order separately).
One medium base lamp,
100w max.

HANGING LANTERN

P6504-122 Aged Copper
Decorative bottom grill included.
8-1/2" dia., 14-1/8" ht.
Overall ht. w/chain 88"; wire 15'.
One medium base lamp,
100w max.

EXTRA LARGE WALL LANTERN

P6606-122 Aged Copper
12-1/2" W., 23-1/2" ht.
Extends 16-5/8". H/CTR 7-5/8".
One medium base lamp,
100w max.

DECORATIVE GRILL

P8789-122 Aged Copper
Decorative Grill for (8.5")
Wall Lantern (P5988-122)
7-1/4" dia., 3/16" ht.



P5988-122



P6504-122



P6504-122
alternate view

Grill included
with P6504-122



P5989-122



P5987-122



P6606-122



P6404-122



P8789-122



*Shown: P6504-122 hanging lantern,
P5988-122 wall lantern and P6404-122 post lantern*

MEADOWLARK



Arched roof, ribbon scrolled loops and arching arms with water seeded glass. Cast aluminum construction with powder coat finish in Oil Rubbed Bronze.

FINISH

- Oil Rubbed Bronze - 108

POST LANTERN

P5468-108 Oil Rubbed Bronze
6-7/8" L., 8-1/2" W., 17-7/8" ht.
Fits 3" post (order separately).
Three candelabra base lamps,
each 60w max.

HANGING LANTERN

P5502-108 Oil Rubbed Bronze
8-1/2" W., 6-7/8" L., 15" ht.
Overall ht. w/chain 90", wire 15'.
Three candelabra base lamps,
each 60w max.

SMALL WALL LANTERN

P5715-108 Oil Rubbed Bronze
6-3/8" W., 12" ht.
Extends 6-7/8". H/CTR 7-5/8".
One medium base lamp,
100w max.

MEDIUM WALL LANTERN

P5716-108 Oil Rubbed Bronze
7-1/4" W., 14-1/2" ht.
Extends 8-1/4". H/CTR 7-3/4".
Two candelabra base lamps,
each 60w max.

LARGE WALL LANTERN

P5717-108 Oil Rubbed Bronze
8-1/2" W., 17-1/8" ht.
Extends 9-5/8". H/CTR 9".
Three candelabra base lamps,
each 60w max.



P5715-108



P5502-108



P5716-108



P5468-108



P5717-108



A gracious cast pattern. Clear seeded glass with delicate, decorative paisley scrolled details. Cast aluminum construction with powder coat finish in espresso.

FINISH

- Espresso - 84



MEDIUM WALL LANTERN

P5959-84 Espresso
8-1/8" sq., 15-1/8" ht.
Extends 10". H/CTR 5-3/4".
One medium base lamp,
100w max.

POST LANTERN

P6401-84 Espresso
9-1/2" sq., 20-3/4" ht.
Fits 3" post (order separately).
One medium base lamp,
100w max.

LARGE WALL LANTERN

P5966-84 Espresso
9-1/2" sq., 18-5/8" ht.
Extends 12". H/CTR 8-3/4".
One medium base lamp,
100w max.

HANGING LANTERN

P6501-84 Espresso
9-1/2" sq., 15" ht. Overall
ht. w/chain 87"; wire 15'.
One medium base lamp,
100w max.



SMALL WALL LANTERN

P5967-84 Espresso
6" sq., 10" ht.
Extends 7-1/2". H/CTR 4-1/4".
One medium base lamp,
100w max.

EXTRA-LARGE WALL LANTERN

P5996-84 Espresso
11" sq., 21-3/4" ht.
Extends 14". H/CTR 10".
One medium base lamp,
100w max.

PRESTWICK



Classic rooflines and unique cast yoke straps in Oil Rubbed Bronze finish. Water glass urn shade.

FINISH

- Oil Rubbed Bronze - 108

POST LANTERN

P5484-108 Oil Rubbed Bronze
10-3/4" dia., 18-3/4" ht.
Fits 3" post (order separately).
Three candelabra base lamps,
each 60w max.

HANGING LANTERN

P5584-108 Oil Rubbed Bronze
10-3/4" dia., 17-3/4" ht.
Overall ht. w/chain 93", wire 15'.
Three candelabra base lamps,
each 40w max.

SMALL WALL LANTERN

P5920-108 Oil Rubbed Bronze
6-7/8" W., 11" ht.
Extends 8". H/CTR 5-1/4".
One medium base lamp,
100w max.

MEDIUM WALL LANTERN

P5921-108 Oil Rubbed Bronze
8-3/4" W., 13-7/8" ht.
Extends 10". H/CTR 6-3/4".
Two candelabra base lamps,
each 60w max.

LARGE WALL LANTERN

P5923-108 Oil Rubbed Bronze
10-3/4" W., 16-3/4" ht.
Extends 12". H/CTR 7-7/8".
Three candelabra base lamps,
each 60w max.



P5920-108



P5584-108



P5921-108



P5484-108



P5923-108



Shown: P5923-108 lanterns

REFUGE



A Cape Cod-inspired frame pays homage to a classic nautical style. Light output and geometric forms offer visual interest to outdoor exteriors. Clear glass windows are paired with a unique amber glass reflector panel on wall lanterns.

FINISH

- Oil Rubbed Bronze - 108

SMALL WALL LANTERN

P6030-108 Oil Rubbed Bronze
6-1/2" W., 13-1/4" ht.
Extends 6-7/8". H/CTR 4-1/4".
One medium base lamp,
100w max.

MEDIUM WALL LANTERN

P6031-108 Oil Rubbed Bronze
8" W., 16" ht.
Extends 8-1/8". H/CTR 5-3/4".
One medium base lamp,
100w max.

LARGE WALL LANTERN

P6032-108 Oil Rubbed Bronze
10-1/2" W., 21" ht.
Extends 10". H/CTR 7-1/2".
One medium base lamp,
100w max.

*Fixtures shown with
P7825-01, page 832.*

POST LANTERN

P6431-108 Oil Rubbed Bronze
8" dia., 18-5/8" ht.
Fits 3" post (order separately).
One medium base lamp,
100w max.

HANGING LANTERN

P6531-108 Oil Rubbed Bronze
8" dia., 16" ht.
Overall ht. w/chain 91"; wire 10'.
One medium base lamp,
100w max.



P6030-108



P6531-108



P6031-108



P6431-108



P6032-108



Signal Bay incorporates nautical design elements in a cast aluminum frame. Clear seeded glass and an Oil Rubbed Bronze finish complete the line.

FINISH

- Oil Rubbed Bronze - 108



POST LANTERN

P5421-108 Oil Rubbed Bronze
10" dia., 16-3/8" ht.
Fits 3" post (order separately).
One medium base lamp,
100w max.

LARGE WALL LANTERN

P5619-108 Oil Rubbed Bronze
13-3/8" W., 14-3/4" ht.
Extends 13-3/8". H/CTR 6-3/8".
One medium base lamp,
100w max.

HANGING LANTERN

P5521-108 Oil Rubbed Bronze
8" dia., 12-3/4" ht.
Overall ht. w/chain 88"; wire 10'.
One medium base lamp,
100w max.

FLUSH MOUNT

P5638-108 Oil Rubbed Bronze
12" dia., 8-1/4" ht.
One medium base lamp,
100w max.

SMALL WALL LANTERN


P5614-108 Oil Rubbed Bronze
6" W., 9-1/4" ht.
Extends 8-1/4". H/CTR 5-1/2".
One medium base lamp,
100w max.

MEDIUM WALL LANTERN

P5618-108 Oil Rubbed Bronze
8" W., 12" ht.
Extends 10-3/4". H/CTR 6-3/8".
One medium base lamp,
100w max.



BOTTA



Botta's styling complements interiors and exteriors with vintage flair. Finely crafted accents highlight clear seeded glass and an Antique Bronze finish.

FINISH

- Antique Bronze - 20

SMALL HANGING LANTERN

P5560-20 Antique Bronze
6-1/4" dia., 9-3/4" ht.
Overall ht. w/chain 76"; wire 15'.
One medium base lamp,
100w max.

MEDIUM HANGING LANTERN

P5561-20 Antique Bronze
7-3/4" dia., 12" ht.
Overall ht. w/chain 78"; wire 15'.
One medium base lamp,
100w max.

SMALL WALL LANTERN

P6043-20 Antique Bronze
6-1/4" W., 11-5/8" ht.
Extends 6-1/2". H/CTR 8-7/8".
One medium base lamp,
100w max.

MEDIUM WALL LANTERN

P6050-20 Antique Bronze
7-3/4" W., 13-7/8" ht.
Extends 8-3/8". H/CTR 11".
One medium base lamp,
100w max.



P6043-20



P5560-20



P6050-20



P5561-20

ARCHIVES



Vintage Electric design with a double shade – clear-seeded oval glass surrounds opal glass and natural brass rods.

FINISH

- Antique Bronze - 20

HANGING LANTERN

P5564-20 Antique Bronze
7-7/8" dia., 12-7/8" ht.
Overall ht. w/chain 79"; wire 15'.
One medium base lamp,
100w max.

MEDIUM WALL LANTERN

P5615-20 Antique Bronze
7-7/8" W., 15-3/8" ht.
Extends 8". H/CTR 3-1/4".
One medium base lamp,
100w max.



P5615-20



P5564-20

DESIGN+SERIES
CREIGHTON



P550009-031



P550009-020



P560031-031



P560031-020



P560032-031



P560032-020



P560033-031



P560033-020



P540009-031



P540009-020



Creighton features clear water glass clear and Antique Bronze or Black finish options. The frame's linear details are riveted to enhance mechanical detailing of the fixture. Wall, post and hanging lantern options available.

FINISHES

- Antique Bronze - 020
- Textured Black - 031

POST LANTERN

P540009-020 Antique Bronze
P540009-031 Black
 10-1/2" dia., 21-3/4" ht.
 Fits 3" post (order separately).
 One medium base lamp,
 100w max.

MEDIUM WALL-LANTERN

P560032-020 Antique Bronze
P560032-031 Black
 8-3/8" W., 15-3/4" ht.
 Extends 9-3/8". H/CTR 3".
 One medium base lamp,
 100w max.

HANGING LANTERN

P550009-020 Antique Bronze
P550009-031 Black
 10-1/2" dia., 21-5/8" ht.
 Overall ht. w/chain 96-1/2"; wire 10'.
 One medium base lamp,
 100w max.

LARGE WALL-LANTERN

P560033-020 Antique Bronze
P560033-031 Black
 10-1/2" W., 19-1/4" ht.
 Extends 11-1/8". H/CTR 3".
 One medium base lamp,
 100w max.

SMALL WALL-LANTERN

P560031-020 Antique Bronze
P560031-031 Black
 6" W., 11-1/2" ht.
 Extends 7-1/4". H/CTR 2-3/8".
 One medium base lamp,
 100w max.

UNION SQUARE



P550007-135



P560004-135

Union Square features a reproduction gas lantern inspiration. A Stainless Steel finish complements the natural polished material and clear flat glass panels. Mechanical details – such as exaggerated knobs – provide character to the form. Open bottom on wall lanterns provides easy access for cleaning and relamping.

FINISH

- Stainless Steel - 135

FLUSH MOUNT

P550007-135 Stainless Steel
12-3/8" sq., 5-1/2" ht.
Two medium base lamps,
each 60w max.

SMALL WALL-LANTERN

P560004-135 Stainless Steel
6-1/2" W., 15-7/8" ht.
Extends 5-1/2". H/CTR 6-1/4".
One medium base lamp,
100w max.

MEDIUM WALL-LANTERN

P560005-135 Stainless Steel
7-7/8" W., 19-3/8" ht.
Extends 6-1/2". H/CTR 7-3/4".
One medium base lamp,
100w max.

LARGE WALL-LANTERN

P560006-135 Stainless Steel
9-3/4" W., 23-5/8" ht.
Extends 8". H/CTR 9-5/8".
One medium base lamp,
100w max.



P560005-135



P560006-135

*Lanterns shown with
P7827-01, page 832.*



Enjoy the simple elegance of traditional styling. Township's clear beveled glass and Oil Rubbed Bronze finish contains notes of New England-inspired style for this charming outdoor lantern collection.

FINISH

● Oil Rubbed Bronze - 108

POST LANTERN

P5404-108 Oil Rubbed Bronze
8" dia., 22-1/2" ht.
Fits 3" post (order separately).
Three candelabra base lamps,
each 60w max.

HANGING LANTERN

P5504-108 Oil Rubbed Bronze
8" dia., 19-3/8" ht.
Overall ht. w/chain 94"; wire 10'.
Three candelabra base lamps,
each 60w max.

SMALL WALL LANTERN

P5692-108 Oil Rubbed Bronze
5-1/2" W., 14-3/4" ht.
Extends 8". H/CTR 3-3/4".
One medium base lamp,
60w max.


MEDIUM WALL LANTERN

P5693-108 Oil Rubbed Bronze
6-1/2" W., 17-1/2" ht.
Extends 8-3/8". H/CTR 3-3/4".
Two candelabra base lamps,
each 60w max.

LARGE WALL LANTERN

P5699-108 Oil Rubbed Bronze
8" W., 22" ht.
Extends 10-1/2". H/CTR 4-1/4".
Three candelabra base lamps,
each 60w max.

GIBBES STREET



Elongated frames capture the romantic charm of vintage gas lanterns. Inspired by a stroll down a Charlestonian street bearing the same name, the Gibbes Street outdoor lantern collection features clear beveled glass and an Antique Bronze finish. Wall, post and hanging lanterns complete the family.

FINISH

● Antique Bronze - 020

POST LANTERN

P540004-020 Antique Bronze
9-1/2" dia., 26-7/8" ht.
Fits 3" post (order separately).
Three candelabra base lamps,
each 60w max.

MEDIUM WALL LANTERN

P560022-020 Antique Bronze
7" W., 21-3/4" ht.
Extends 8-3/4". H/CTR 8-3/8".
Two candelabra base lamps,
each 60w max.

HANGING LANTERN

P550004-020 Antique Bronze
9-1/2" dia., 23-3/4" ht.
Overall ht. w/chain 99"; wire 10'.
Three candelabra base lamps,
each 60w max.

LARGE WALL LANTERN

P560023-020 Antique Bronze
9-1/2" W., 30-5/8" ht.
Extends 11-1/4". H/CTR 10-3/4".
Three candelabra base lamps,
each 60w max.

SMALL WALL LANTERN

P560021-020 Antique Bronze
5-1/2" W., 15-1/8" ht.
Extends 7". H/CTR 5-7/8".
One medium base lamp,
100w max.

*Lanterns shown with P7826-01,
page 832 except where noted.*



P560021-020
shown with P7827-01
vintage lamp



P550004-020



P560022-020



P540004-020



P560023-020



P560002-020
*shown with P7826-01
 vintage lamps*



P560002-031
*shown with P7826-01
 vintage lamps*



P560003-020



P560003-031
*shown with P7826-01
 vintage lamps*



A classic colonial wall lantern with contemporary touches describes Santee. Featuring a geometric frame and graphic handle, the wider beveled glass offers more refraction – and visual interest – than typical lantern designs. Choose from a Black frame with stainless steel candle option or an Antique Bronze frame with painted brass candle option.

FINISHES

- Antique Bronze - 020
- Black - 031

SMALL WALL LANTERN

P560002-020 Antique Bronze
P560002-031 Black
 8" W., 15-1/4" ht.
 Extends 5-3/4". H/CTR 8-3/4".
 Two candelabra base lamps,
 each 60w max.

LARGE WALL LANTERN

P560003-020 Antique Bronze
P560003-031 Black
 9-1/2" W., 19-5/8" ht.
 Extends 6-1/2". H/CTR 11-3/8".
 Three candelabra base lamps,
 each 60w max.

DESIGN+SERIES
KIAWAH



Seeded glass panels and traditional detailing combine to create a soft and updated lantern design. Hinged door for easy relamping is available for post, hanging and medium, large and extra large wall lanterns.

FINISH

● Black - 031

POST LANTERN

P540001-031 Black
 9-1/2" sq., 20-7/8" ht.
 Fits 3" post (order separately).
 Three candelabra base lamps,
 each 60w max.

HANGING LANTERN

P550001-031 Black
 9-1/2" sq., 19-5/8" ht.
 Overall ht. w/chain 94-1/2"; wire 10'.
 Three candelabra base lamps,
 each 60w max.

SMALL WALL LANTERN

P560010-031 Black
 5-5/8" W., 12-7/8" ht.
 Extends 6-3/8". H/CTR 5-3/8".
 One medium base lamp,
 100w max.

MEDIUM WALL LANTERN

P560011-031 Black
 7-1/2" W., 21-7/8" ht.
 Extends 8-3/8". H/CTR 8-1/4".
 Two candelabra base lamps,
 each 60w max.

LARGE WALL LANTERN

P560012-031 Black
 9-1/2" W., 27-1/4" ht.
 Extends 10-1/4". H/CTR 10".
 Three candelabra base lamps,
 each 60w max.

**EXTRA-LARGE
 WALL LANTERN**

P560013-031 Black
 12-1/2" W., 34-1/2" ht.
 Extends 13-1/2". H/CTR 10-3/4".
 Three candelabra base lamps,
 each 60w max.



P560010-031



P550001-031



P560012-031




P560011-031



P560013-031



P540001-031



Endorse celebrates the traditional form of a gas-powered coach light with illumination from a modern LED source. A die-cast aluminum, powder coated frame creates an intriguing visual effect with clear beveled glass. To add a decorative element in the lantern, a fluted frosted glass column is offered as an accessory.

FINISH

- Black - 31

SMALL WALL LANTERN

P6056-3130K9 Black
6-3/4" W., 12" ht.
Extends 7-5/8". H/CTR 3-1/4".
One 9w LED module included.



MEDIUM WALL LANTERN

P6057-3130K9 Black
8-3/4" W., 14-3/4" ht.
Extends 9-3/4". H/CTR 4".
One 9w LED module included.



LARGE WALL LANTERN

P6058-3130K9 Black
10-3/4" W., 17-3/4" ht.
Extends 11-3/4". H/CTR 4".
One 9w LED module included.



HANGING LANTERN

P6526-3130K9 Black
8-3/4" sq., 14-1/2" ht.
Overall ht. w/chain 101"; wire 12'.
One 9w LED module included.



SMALL ACCESSORY COLUMN

P8774-31 Black
For use with P6056
2-3/4" sq., 9-5/8" ht.

MEDIUM ACCESSORY COLUMN

P8775-31 Black
For use with P6057 & P5686
2-3/4" sq., 12-3/8" ht.

LARGE ACCESSORY COLUMN

P8779-31 Black
For use with P6058
2-3/4" sq., 15-1/4" ht.

LED FEATURES

- 120v AC, replaceable module
- 623 lumens, 69.2 lumens/watt
- 3000K color temperature; 90 CRI
- Dimmable to 10% brightness with many ELV type dimmers



BROOKSIDE



Get inspired from vintage undertones and train station styling with this outdoor lantern collection. Available in aluminum with Gilded Iron finish or solid brass Antique Nickel or solid Copper that ages to a patina finish. Dark Sky compliant.

FINISHES

- Copper - 14
- Gilded Iron - 71
- Antique Nickel - 81

SMALL WALL LANTERN

P5721-14 Copper

P5721-71 Gilded Iron

P5721-81 Antique Nickel

8" W., 9-3/4" ht.

Extends 9-3/4". H/CTR 5-3/4".

One medium base lamp,
60w max.

MEDIUM WALL LANTERN

P5722-14 Copper

P5722-71 Gilded Iron

P5722-81 Antique Nickel

10" W., 10-3/4" ht.

Extends 11-3/4". H/CTR 6-1/2".

One medium base lamp,
75w max.

LARGE WALL LANTERN

P5723-14 Copper

P5723-71 Gilded Iron

P5723-81 Antique Nickel

12" W., 12-3/8" ht.

Extends 13-1/8". H/CTR 6-7/8".

One medium base lamp,
100w max.



P5721-81



P5721-14



P5722-81



P5722-14



P5723-81



P5723-14



P5721-71



P5722-71



P5723-71



P5723-1430K9



P5723-7130K9

FINISHES

- Copper - 14
- Gilded Iron - 71
- Antique Nickel - 81

LARGE WALL LANTERN

P5723-1430K9 Copper

P5723-7130K9 Gilded Iron

P5723-8130K9 Antique Nickel

12" W., 12-1/4" ht.

Extends 13-1/4". H/CTR 6-7/8".

One 17w LED module included.



P5723-8130K9

LED FEATURES

- 120v AC, replaceable module
- 1211 lumens, 71.2 lumens/watt
- 3000K color temperature; 90 CRI
- Dimmable to 10% brightness with many ELV type dimmers

PROGRESS **LED**

Shown: P5723-81 lanterns



ANDOVER

Beveled glass panels. Die-cast aluminum construction in an Antique Bronze finish.

FINISH

● Antique Bronze - 20

POST LANTERN*

P5487-20 Antique Bronze
9-1/2" sq., 21-1/2" ht.
Fits 3" post (order separately).
Three candelabra base lamps,
each 60w max.

HANGING LANTERN*

P5587-20 Antique Bronze
9-1/2" sq., 20" ht.
Overall ht. w/chain 94"; wire 10'.
Three candelabra base lamps,
each 60w max.

EXTRA-LARGE WALL LANTERN*

P5627-20 Antique Bronze
12-1/2" W., 34-1/2" ht.
Extends 13-1/2". H/CTR 11-3/4".
Four candelabra base lamps,
each 60w max.

SMALL WALL LANTERN

P5687-20 Antique Bronze
5-1/2" W., 12-3/4" ht.
Extends 6-1/4". H/CTR 6-1/4".
One medium base lamp,
100w max.

MEDIUM WALL LANTERN*

P5688-20 Antique Bronze
7-1/2" W., 21-1/4" ht.
Extends 8-1/4". H/CTR 7-1/2".
Two candelabra base lamps,
each 60w max.

LARGE WALL LANTERN*

P5689-20 Antique Bronze
9-1/2" W., 26-1/4" ht.
Extends 10-1/4". H/CTR 9".
Three candelabra base lamps,
each 60w max.

*Hinged door for easy relamping.



P5687-20



P5587-20



P5689-20



P5688-20



P5627-20



P5487-20



Clear seeded water glass panes with etched pillar diffuser. GU24 sockets for use with energy efficient lamps.

FINISH

● Black - 31

POST LANTERN

P6438-31 Black
9-1/2" dia., 22-3/8" ht.
Fits 3" post (order separately).
One GU24 lamp,
26w max.



HANGING LANTERN

P6538-31 Black
12-1/2" dia., 25-1/4" ht.
Overall ht. w/chain 100-1/2", wire 10'.
One GU24 lamp,
26w max.



SMALL WALL LANTERN

P6619-31 Black
5-5/8" W., 13-3/8" ht.
Extends 6-3/4". H/CTR 6-3/8".
One GU24 lamp,
18w max.



MEDIUM WALL LANTERN

P6620-31 Black
7-1/2" W., 18-3/8" ht.
Extends 8-3/8". H/CTR 10-1/2".
One GU24 lamp,
26w max.



LARGE WALL LANTERN

P6621-31 Black
9-1/2" W., 26-1/4" ht.
Extends 10-1/4". H/CTR 12-3/4".
One GU24 lamp,
26w max.



EXTRA-LARGE WALL LANTERN

P6622-31 Black
12-1/2" W., 34-3/8" ht.
Extends 13-1/2". H/CTR 18-5/8".
One GU24 lamp,
26w max.



COVENTRY

Capture the romance with optic hammered glass, stylized cap and shepherd's crook support arm. Die-cast aluminum construction.

FINISHES

● Textured Black - 31

● Fieldstone - 87

PAIR WITH

Path Light, page 741

POST LANTERN

P5429-31 Textured Black

P5429-87 Fieldstone

9-3/4" dia., 19-5/8" ht.

Fits 3" post (order separately).

Two candelabra base lamps, each 60w max.

HANGING LANTERN

P5529-31 Textured Black

P5529-87 Fieldstone

9-3/4" dia., 19-1/4" ht.

Overall ht. w/chain 94"; wire 10'.

Two candelabra base lamps, each 60w max.

MEDIUM WALL LANTERN

P5828-31 Textured Black

P5828-87 Fieldstone

8" W., 17-1/4" ht.

Extends 10". H/CTR 10".

One medium base lamp, 100w max.

LARGE WALL LANTERN

P5829-31 Textured Black

P5829-87 Fieldstone

9-3/4" W., 20-1/2" ht.

Extends 12-1/2". H/CTR 12".

Two candelabra base lamps, each 60w max.



P5529-31



P5529-87



P5828-31



P5828-87



P5829-31



P5829-87



P5429-31



P5429-87



Shown: P5829-87 lanterns

ONION LANTERNS

Detailed finials, end caps and scrollwork in powder coat Black finish, featuring clear beveled glass and cast aluminum frames.

FINISH

- Black - 31

POST LANTERN

P5401-31 Black
11-1/8" dia., 27-3/4" ht.
Fits 3" post (order separately).
Four candelabra base lamps,
each 60w max.

HANGING LANTERN

P5501-31 Black
11-1/8" dia., 28" ht.
Overall ht. w/chain 102"; wire 15'.
Four candelabra base lamps,
each 60w max.

MEDIUM WALL LANTERN

P5700-31 Black
7-3/4" W., 23-1/4" ht.
Extends 10-3/4".
Three candelabra base lamps,
each 60w max.

LARGE WALL LANTERN

P5701-31 Black
Four-light wall lantern.
11-1/8" W., 31" ht.
Extends 16".
Four candelabra base lamps,
each 60w max.

SMALL WALL LANTERN

P5878-31 Black
6-1/2" W., 21-1/4" ht.
Extends 10". H/CTR 13-1/8".
One medium base lamp,
100w max.



P5878-31



P5501-31



P5700-31



P5701-31



P5701-31



Edition features clear water glass elements and a die-cast aluminum, powder coated frame. The distinct hexagonal shape offers a classical style to consider for updating a home's curb appeal.

FINISHES

- Antique Bronze - 20
- Black - 31

SMALL WALL LANTERN

P6070-20 Antique Bronze
P6070-31 Black
 5-1/2" W., 9-1/8" ht.
 Extends 6-1/2". H/CTR 2-3/4".
 One medium base lamp,
 100w max.

MEDIUM WALL LANTERN

P6071-20 Antique Bronze
P6071-31 Black
 7-1/8" W., 12-1/2" ht.
 Extends 8-1/8". H/CTR 3-1/8".
 One medium base lamp,
 100w max.

LARGE WALL LANTERN

P6072-20 Antique Bronze
P6072-31 Black
 9" W., 15-7/8" ht.
 Extends 10". H/CTR 4-1/16".
 One medium base lamp,
 100w max.

POST LANTERN

P6429-20 Antique Bronze
P6429-31 Black
 9" W., 21-7/8" ht.
 Fits 3" post (order separately).
 One medium base lamp,
 100w max.

HANGING LANTERN

P6529-20 Antique Bronze
P6529-31 Black
 7-1/8" dia., 13" ht.
 Overall ht. w/chain 88"; wire 180".
 One medium base lamp,
 100w max.

WELBOURNE

Hexagonal cast aluminum framework with vine-inspired scrolls. Beveled clear glass panels in Textured Black or Textured White finishes.

FINISHES

- White - 30
- Black - 31

POST LANTERN

P5482-30 Textured White
P5482-31 Textured Black
 9-1/2" dia., 21-1/4" ht.
 Fits 3" post (order separately).
 One medium base lamp,
 100w max.

LARGE POST LANTERN

P5483-31 Textured Black
 13" dia., 26" ht.
 Fits 3" post (order separately).
 Three candelabra base lamps,
 60w max.

HANGING LANTERN

P5582-30 Textured White
P5582-31 Textured Black
 9-1/2" dia., 15" ht. Overall ht.
 w/ chain 51"; wire 10'
 One medium base lamp,
 100w max.

SMALL WALL LANTERN

P5681-30 Textured White
P5681-31 Textured Black
 6-1/2" W., 16-7/8" ht.
 Extends 9-1/4". H/CTR 13-1/4".
 One medium base lamp,
 100w max.

SMALL WALL LANTERN

P5682-30 Textured White
P5682-31 Textured Black
 6-1/2" W., 13-1/4" ht.
 Extends 9". H/CTR 3-1/2".
 One medium base lamp,
 100w max.

MEDIUM WALL LANTERN

P5683-31 Textured Black
 9-1/2" W., 18" ht.
 Extends 9-3/4" H/CTR 8-1/2".
 One medium base lamp,
 100w max.

MEDIUM WALL LANTERN

P5684-31 Textured Black
 Use with or without tail.
 9-1/2" W., 30-3/4" ht.
 with tail. 23-1/4" ht. without tail.
 Extends 11-3/8". H/CTR 18-3/8"
 One medium base lamp,
 100w max.

LARGE WALL LANTERN

P5690-31 Textured Black
 13" W., 22-1/4" ht.
 Extends 14". H/CTR 5".
 Three candelabra base lamps,
 each 60w max.



P5681-30



P5582-30



P5682-30



P5482-30



P5483-30



P5582-31



P5682-31



P5681-31



P5482-31



P5683-31



P5684-31
shown without tail



P5483-31



P5690-31



P5684-31
shown with tail

PEDIGREE



Durable powder coat finish. Cast pyramidal block and fluted uprights. Energy efficient outdoor lanterns with etched seeded glass. Cast aluminum construction in an Autumn Haze finish.

FINISH

● Autumn Haze - 97

SMALL WALL LANTERN

P5980-97 Autumn Haze
7" W., 10" ht.
Extends 8-1/2". H/CTR 2-5/8".
One GU24 base CFL lamp,
26w max.



MEDIUM WALL LANTERN

P5981-97 Autumn Haze
9" W., 13-3/8" ht.
Extends 10-1/2". H/CTR 5-3/4".
One GU24 base CFL lamp,
26w max.



LARGE WALL LANTERN

P5982-97 Autumn Haze
11-1/2" W., 16-1/2" ht.
Extends 13-1/2". H/CTR 5-3/4".
One GU24 base lamp,
26w max.



POST LANTERN

P6403-97 Autumn Haze
9" dia., 16-3/8" ht.
Fits 3" post (order separately).
One GU24 base CFL lamp,
26w max.



HANGING LANTERN

P6503-97 Autumn Haze
9" dia., 13-5/8" ht.
Overall ht w/chain 88"; wire 15'.
One GU24 base CFL lamp,
26w max.



EXTRA LARGE WALL LANTERN

P6607-97 Autumn Haze
13-1/2" W., 19-3/8" ht.
Extends 15-3/4". H/CTR 6-3/4".
One GU24 base CFL lamp,
42w max.



P5980-97



P6503-97



P5981-97



P5982-97



P6607-97



P6403-97



Square etched opal shades suspended in a rectilinear framework. Steel construction with Antique Bronze powder coat finish.

FINISH

● Antique Bronze - 20

POST LANTERN

P5490-20 Antique Bronze
9-7/8" L., 7-3/4" W., 15-1/2" ht. Fits
3" post (order separately).
One medium base lamp,
100w max.

HANGING LANTERN

P5590-20 Antique Bronze
9-7/8" L., 7-3/4" W., 16-1/2" ht.,
Overall ht. w/chain 91"; wire 10'.
One medium base lamp,
100w max.

SMALL WALL LANTERN

P5990-20 Antique Bronze
7-3/4" W., 14" ht.
Extends 5-5/8". H/CTR 7".
One medium base lamp,
100w max.

MEDIUM WALL LANTERN

P5991-20 Antique Bronze
9-3/4" W., 16-1/2" ht.
Extends 6-1/2". H/CTR 8-1/4".
One medium base lamp,
100w max.

LARGE WALL LANTERN

P5992-20 Antique Bronze
11-3/4" W., 18" ht.
Extends 7-1/4". H/CTR 9".
One medium base lamp,
100w max.



DESIGN+SERIES TWAIN



Featuring an updated prairie style, Twain's lantern collection offers visual interest for a variety of home exteriors. Solid glass with the center sand blasted, is divided by the frames vertical lines.

FINISH

● Antique Bronze - 020

POST LANTERN

P540000-020 Antique Bronze
7-3/4" sq., 16" ht.
Fits 3" post (order separately).
One medium base lamp,
100w max.

HANGING LANTERN

P550000-020 Antique Bronze
7-3/4" sq., 13-3/4" ht.
Overall ht. w/chain 88-1/2"; wire 10'.
One medium base lamp,
100w max.

SMALL WALL LANTERN

P560007-020 Antique Bronze
5-3/4" W., 10-1/4" ht.
Extends 6-3/4". H/CTR 2-3/8".
One medium base lamp,
100w max.

MEDIUM WALL LANTERN

P560008-020 Antique Bronze
7-3/4" W., 13-1/2" ht.
Extends 8-7/8". H/CTR 2-3/4".
One medium base lamp,
100w max.

LARGE WALL LANTERN

P560009-020 Antique Bronze
9-1/2" W., 16-1/2" ht.
Extends 10-3/4". H/CTR 3-1/4".
One medium base lamp,
100w max.



P560007-020



P550000-020



P560008-020



P540000-020



P560009-020

ARRIVE



Arrive LED lanterns feature a die-cast aluminum powder coated frame and heavily textured glass to create a unique visual effect.

FINISH

- Black - 31

PATH LIGHT

P5258-31 Black
5" dia., 6-1/2" ht.
Must use with transformer.
One 12v T5 wedge base,
18w max., included.

**POST LANTERN**

P6427-3130K9 Black
9" sq., 15-7/8" ht.
Fits 3" post (order separately).
One 17w LED module included.

**SMALL WALL LANTERN**

P6067-3130K9 Black
6" W., 8-3/4" ht.
Extends 7-3/8". H/CTR 4".
One 9w LED module included.

**HANGING LANTERN**

P6527-3130K9 Black
9" sq., 15-1/8" ht. Overall ht.
w/chain 88-1/4"; wire 15".
One 17w LED module included.

**MEDIUM WALL LANTERN**

P6068-3130K9 Black
7-1/2" W., 11-1/8" ht.
Extends 8-3/4". H/CTR 5-1/4".
One 9w LED module included.

**LARGE WALL LANTERN**

P6069-3130K9 Black
9" W., 13" ht.
Extends 10-1/4". H/CTR 5-3/4".
One 17w LED module included.

**EXTRA LARGE WALL LANTERN**

P6076-3130K9 Black
11" W., 16" ht.
Extends 12-1/4". H/CTR 8-5/8".
One 17w LED module included.

**LED FEATURES**

- 120v AC, replaceable module
- 9w: 623 lumens, 69.2 lumens/watt
17w: 1211 lumens, 71.2 lumens/watt
- 3000K color temperature; 90 CRI
- Dimmable to 10% brightness with many ELV type dimmers

PROGRESS **LED**

DERBY

Derby boasts a combination of Espresso and Textured Black powder coat finishes. Features a blown, clear seeded glass diffuser encased in a cast aluminum black frame. Espresso finish on roof and back plate.

FINISH

● Espresso - 84

POST LANTERN

P5479-84 Espresso
8-1/2" dia., 13-3/8" ht.
Fits 3" post (order separately).
One medium base lamp,
100w max.

HANGING LANTERN

P5579-84 Espresso
8-1/2" dia., 12-3/8" ht.,
Overall ht. w/chain 86"; wire 15'.
One medium base lamp,
100w max.

SMALL WALL LANTERN

P5749-84 Espresso
6-1/2" W., 8-3/8" ht.
Extends 7-5/8". H/CTR 3".
One medium base lamp,
100w max.

MEDIUM WALL LANTERN

P5750-84 Espresso
8-1/2" W., 11" ht.
Extends 9-5/8". H/CTR 4-1/4".
One medium base lamp,
100w max.

LARGE WALL LANTERN

P5751-84 Espresso
10-5/8" W., 15" ht.
Extends 14-1/8". H/CTR 3-3/8".
One medium base lamp,
100w max.

FLUSH MOUNT

P6017-84 Espresso
10" sq., 5-1/2" ht.
Two medium base lamps,
each 60w max.



P5749-84



P5579-84



P5750-84



P6017-84



P5751-84



P5479-84



P6017-2030K9



P5749-2030K9



P5750-2030K9



P5751-2030K9



Craftsman styling marries traditional and rustic details. Derby boasts an artistic glass diffuser with a die-cast aluminum, powder coated Antique Bronze frame.

FINISH

- Antique Bronze - 20

SMALL WALL LANTERN

P5749-2030K9 Antique Bronze
6-1/2" W., 8-3/8" ht.
Extends 7-3/8". H/CTR 3".
One 9w LED module included.



MEDIUM WALL LANTERN

P5750-2030K9 Antique Bronze
8-1/2" W., 11-1/4" ht.
Extends 9-3/8". H/CTR 4-1/4".
One 9w LED module included.



LARGE WALL LANTERN

P5751-2030K9 Antique Bronze
10-5/8" W., 15-1/2" ht.
Extends 11-5/8". H/CTR 3-3/8".
One 9w LED module included.



FLUSH MOUNT

P6017-2030K9 Antique Bronze
10" sq., 5-1/2" ht.
One 17w LED module included.



LED FEATURES

- 120v AC, replaceable module
- 9w: 623 lumens, 69.2 lumens/watt
- 17w: 1211 lumens, 71.2 lumens/watt
- 3000K color temperature; 90 CRI
- Dimmable to 10% brightness with many ELV type dimmers

PROGRESS **LED**

ENDICOTT

With a Craftsman-inspired silhouette, Endicott offers visual interest. The elongated frame is finished with umber linen glass.

FINISH

● Antique Bronze - 20

POST LANTERN

P5400-20 Antique Bronze
7-3/8" dia., 17-3/4" ht.
Fits 3" post (order separately).
One medium base lamp,
100w max.

HANGING LANTERN

P5500-20 Antique Bronze
7-3/8" dia., 15-1/4" ht.
Overall ht. w/chain 91"; wire 12".
One medium base lamp,
100w max.

SMALL WALL LANTERN

P5605-20 Antique Bronze
7-1/4" W., 10-1/2" ht.
Extends 9-1/2". H/CTR 2-3/4".
One medium base lamp,
100w max.

MEDIUM WALL LANTERN

P5610-20 Antique Bronze
7-1/4" W., 14-1/4" ht.
Extends 9-1/2". H/CTR 3-5/8".
One medium base lamp,
100w max.

LARGE WALL LANTERN

P5611-20 Antique Bronze
8-7/8" W., 12-1/2" ht.
Extends 11". H/CTR 3-5/8".
One medium base lamp,
100w max.

EXTRA LARGE WALL LANTERN

P5613-20 Antique Bronze
8-7/8" W., 18" ht.
Extends 11". H/CTR 4-1/2".
One medium base lamp,
100w max.



P5605-20



P5610-20



P5613-20



P5500-20



P5610-20



P5400-20



A rich earthy palette, geometric details and textured art glass characterize residence – a truly craftsman style with a die-cast aluminum, powder coated frame.

FINISH

● Antique Bronze - 20

SMALL WALL LANTERN

P6052-20 Antique Bronze
6" W., 9-1/4" ht.
Extends 6-7/8". H/CTR 3-1/2".
One medium base lamp,
100w max.

MEDIUM WALL LANTERN

P6053-20 Antique Bronze
8" W., 12-3/8" ht.
Extends 9". H/CTR 5".
One medium base lamp,
100w max.

LARGE WALL LANTERN

P6054-20 Antique Bronze
10" W., 15-3/8" ht.
Extends 11-1/8". H/CTR 5-5/8".
One medium base lamp,
100w max.

FLUSH MOUNT

P6055-20 Antique Bronze
12" W., 5" ht.
Two medium base lamps,
75w max.

POST LANTERN

P6452-20 Antique Bronze
8" W., 15-3/4" ht.
Fits 3" post (order separately).
One medium base lamp,
100w max.

HANGING LANTERN

P6552-20 Antique Bronze
8" sq., 12-5/8" ht.
Overall ht. w/ chain 86-1/4"; wire 10'.
One medium base lamp,
each 100w max.

PENFIELD

Reinvent exterior areas with smooth curves. Highlighted by clear glass exterior surrounding an opal glass interior diffuser. Aluminum and brass construction.

FINISH

- Oil Rubbed Bronze - 108

POST LANTERN

P5472-108 Oil Rubbed Bronze
8" dia., 14-3/4" ht.
Fits 3" post (order separately).
One medium base lamp,
100w max.

HANGING LANTERN

P5503-108 Oil Rubbed Bronze
8" dia., 14-1/4" ht.
Overall ht w/chain 89"; wire 15'.
One medium base lamp,
100w max.

SMALL WALL LANTERN

P5895-108 Oil Rubbed Bronze
6-1/2" W., 9-3/4" ht.
Extends 8-1/2". H/CTR 5".
One medium base lamp,
100w max.

MEDIUM WALL LANTERN

P5896-108 Oil Rubbed Bronze
8" W., 11-3/4" ht.
Extends 10-1/4". H/CTR 6".
One medium base lamp,
100w max.

LARGE WALL LANTERN

P5899-108 Oil Rubbed Bronze
8" W., 24" ht.
Extends 10-3/8". H/CTR 12-1/4".
Two medium base lamps,
each 75w max.



P5895-108



P5896-108



P5899-108



P5503-108



P5472-108



Shown: P5897-108 lanterns

WISH



Wish maximizes aesthetics in outdoor areas for those who desire to preserve the exterior environment. Included dark sky shield provides full cut off illumination or remove for a traditional lighting effect. Antique Bronze finish has etched umber linen glass. Black finish has etched white linen glass.

FINISHES

- Antique Bronze - 20
- Black - 31

SMALL WALL LANTERN

P6084-20 Antique Bronze

P6084-31 Black

7" W., 10-3/8" ht.

Extends 8-5/8". H/CTR 3-1/8".

One medium base lamp,
75w max.



Dark sky cylinder included, except the post lantern.

MEDIUM WALL LANTERN

P6085-20 Antique Bronze

P6085-31 Black

9" W., 12-1/2" ht.

Extends 10-1/2". H/CTR 3-1/8".

One medium base lamp,
100w max.

POST LANTERN

P6424-20 Antique Bronze

P6424-31 Black

Dark Sky shield not included.

9" dia., 15-1/4" ht.

Fits 3" post (order separately).

One medium base lamp,
100w max.

HANGING LANTERN

P6524-20 Antique Bronze

P6524-31 Black

9" dia., 12-1/2" ht.

Overall ht. w/chain 87-1/2"; wire 15'.

One medium base lamp,
100w max.



P6524-31



P6524-20



P6084-31



P6084-20



P6085-31



P6085-20



P6424-31



P6424-20



P6524-2030K9



P6524-3130K9



P6084-2030K9



P6084-3130K9



P6085-2030K9



P6085-3130K9



P6424-2030K9



P6424-3130K9

FINISHES

- Antique Bronze - 20
- Black - 31

SMALL WALL LANTERN

P6084-2030K9 Antique Bronze
P6084-3130K9 Black
 7" W., 10-3/8" ht.
 Extends 8-5/8". H/CTR 3-1/8".
 One 9w LED module included.



MEDIUM WALL LANTERN

P6085-2030K9 Antique Bronze
P6085-3130K9 Black
 9" W., 12-1/2" ht.
 Extends 10-1/2". H/CTR 3-1/8".
 One 17w LED module included.



POST LANTERN

P6424-2030K9 Antique Bronze
P6424-3130K9 Black
 Dark Sky shield not included.
 9" dia., 15-1/4" ht.
 Fits 3" post (order separately).
 One 9w LED module included.



HANGING LANTERN

P6524-2030K9 Antique Bronze
P6524-3130K9 Black
 9" sq., 12-1/2" ht.
 Overall ht. w/chain 87-1/2"; wire 15'.
 One 17w LED module included.



LED FEATURES

- 120V AC, replaceable module
- 9w: 623 lumens, 69.2 lumens/watt
- 17w: 1211 lumens, 71.2 lumens/watt
- 3000K color temperature; 90+ CRI
- TM-21 60,000 hr. life
- Dimmable to 10% brightness with many ELV type dimmers

PROGRESS **LED**



Dark sky cylinder included, except the post lantern.

MAC



Classic Arts and Crafts inspired profile. Cast aluminum construction. clear water glass and Decorative bottom detail. Textured Black powder coated finish.

FINISH

- Black - 31

POST LANTERN

P5459-31 Black
8-1/2" sq., 16-1/2" ht.
Fits 3" post (order separately).
One medium base lamp,
100w max.

HANGING LANTERN

P5559-31 Black
8-1/2" sq., 14-7/8" ht.,
Overall ht. w/chain 87"; wire 15'.
One medium base lamp,
100w max.

SMALL WALL LANTERN

P5906-31 Black
6" sq., 8-1/2" ht.
Extends 7-1/8". H/CTR 5".
One medium base lamp,
100w max.

MEDIUM WALL LANTERN

P5907-31 Black
8-1/2" sq., 12" ht.
Extends 10". H/CTR 6-3/4".
One medium base lamp,
100w max.

LARGE WALL LANTERN

P5999-31 Black
11" sq., 16-3/4" ht.
H/CTR 7-3/4".
One medium base lamp,
100w max.

FLUSH MOUNT

P6023-31 Black
11" sq., 7" ht.
Two medium base lamp,
100w max.



P6023-31



P5559-31



P5907-31



P5906-31



P5999-31



P5459-31

MERIT



P6500-31



P6000-31



Square etched glass shade within rectilinear frame. Cast aluminum construction. Frame showcases pierced grid pattern with Black powder coat finish.

FINISH

- Black - 31

SMALL WALL LANTERN

P6000-31 Black
5-1/4" sq., 8" ht.
Extends 6-1/4". H/CTR 2-1/2".
One medium base lamp,
60w max.

MEDIUM WALL LANTERN

P6001-31 Black
7-3/4" sq., 12-1/4" ht.
Extends 9". H/CTR 3".
One medium base lamp,
100w max.

LARGE WALL LANTERN

P6002-31 Black
10" sq., 15-3/4" ht.
Extends 11-3/8". H/CTR 4".
One medium base lamp,
100w max.

POST LANTERN

P6400-31 Black
10" sq., 18-3/4" ht.
Fits 3" post (order separately).
One medium base lamp,
100w max.

HANGING LANTERN

P6500-31 Black
10" sq., 17" ht.
Overall ht. w/chain 91"; wire 10'.
One medium base lamp,
100w max.



P6400-31




P6001-31



P6002-31

HAWTHORNE



This outdoor lantern collection takes a modern approach to the popular Prairie design style. Available in Antique Bronze with amber seeded glass or Black with etched seeded glass.

FINISHES

- Antique Bronze - 20
- Black - 31

POST LANTERN

P5413-20 Antique Bronze

P5413-31 Black

7-1/2" dia., 17-1/4" ht.

Two candelabra base lamp,
60w max.

SMALL HANGING LANTERN

P5513-20 Antique Bronze

P5513-31 Black

5" dia., 9-1/8" ht.

Overall ht. w/stem 74", wire 10'.

One medium base lamp,
100w max.

LARGE HANGING LANTERN

P5523-20 Antique Bronze

P5523-31 Black

7 1/2" dia., 14-7/8" ht.

Overall ht. w/stem 88", wire 10'.

lamp: one medium base lamp,
100w max.

SMALL WALL LANTERN

P5624-20 Antique Bronze

P5624-31 Black

5" W., 9-5/8" ht.

Extends 6-1/2". H/CTR 2-3/4".

One medium base lamp,
100w max.

MEDIUM WALL LANTERN

P5625-20 Antique Bronze

P5625-31 Black

6" W., 12-5/8" ht.

Extends 8-3/8". H/CTR 3-3/8".

One medium base lamp,
100w max.

LARGE WALL LANTERN

P5665-20 Antique Bronze

P5665-31 Black

7 1/2" W., 16" ht.

Extends 10-3/4". H/CTR 4-1/8".

One medium base lamp,
100w max.





P5624-20



P5624-31



P5413-20



P5625-20



P5625-31



P5413-31



P5665-20



P5665-31

PRAIRIE

Unique cantilevered arms, distinctive roof and clear seeded glass. Aluminum and brass construction in Brushed Nickel, Gilded Iron or Burnished Chestnut finishes.

FINISHES

- Brushed Nickel - 09
- Gilded Iron - 71
- Burnished Chestnut - 86

POST LANTERN

P5463-09 Brushed Nickel*
P5463-71 Gilded Iron
P5463-86 Burnished Chestnut
 13-3/4" W., 18-3/4" ht.
 Fits 3" post (order separately).
 One medium base lamp,
 100w max.

HANGING LANTERN

P5563-09 Brushed Nickel*
P5563-71 Gilded Iron
P5563-86 Burnished Chestnut
 10" dia., 12-1/2" ht.
 Overall ht. w/chain 52"; wire 15'.
 One medium base lamp,
 100w max.

SMALL WALL LANTERN

P5763-09 Brushed Nickel*
P5763-71 Gilded Iron
P5763-86 Burnished Chestnut
 6-3/8" W., 9-1/8" ht.
 Extends 8-1/2". H/CTR 5-1/4".
 One medium base lamp,
 100w max.

MEDIUM WALL LANTERN

P5764-09 Brushed Nickel*
P5764-71 Gilded Iron
P5764-86 Burnished Chestnut
 10" W., 13-1/2" ht.
 Extends 12-1/2". H/CTR 7-1/2".
 One medium base lamp,
 100w max.

*Brass construction



P5563-09



P5563-71



P5563-86



P5763-09



P5763-71



P5763-86



P5764-09



P5764-71



P5764-86



P5463-09



P5463-71



P5463-86



P6512-20



P6512-31



P6059-20



P6059-31



P6060-20



P6060-31



P6086-20



P6086-31



P6412-20



P6412-31



White linen glass is completed with a powder coated aluminum frame and Black finish, while an amber linen glass shade complements the warm Antique Bronze finish.

FINISHES

- Antique Bronze - 20
- Black - 31

SMALL WALL LANTERN

P6059-20 Antique Bronze
P6059-31 Black
 5-7/8" W., 8-3/4" ht.
 Extends 6-3/4". H/CTR 2-1/4".
 One medium base lamp,
 100w max.

MEDIUM WALL LANTERN

P6060-20 Antique Bronze
P6060-31 Black
 8" W., 11-1/8" ht.
 Extends 8-7/8". H/CTR 2-1/4".
 One medium base lamp,
 100w max.

LARGE WALL LANTERN

P6086-20 Antique Bronze
P6086-31 Black
 10" W., 13-7/8" ht.
 Extends 11-1/8". H/CTR 2-3/8".
 One medium base lamp,
 100w max.

POST LANTERN

P6412-20 Antique Bronze
P6412-31 Black
 10" dia., 18-3/8" ht.
 Fits 3" post (order separately).
 Three candelabra base lamps,
 each 60w max.

HANGING LANTERN

P6512-20 Antique Bronze
P6512-31 Black
 8" dia., 11-1/2" ht.
 Overall ht. w/chain 87"; wire 15'.
 One medium base lamp,
 100w max.

ARTS & CRAFTS



Reminisce under lighting inspired by the bungalows of the 1900's. Charming highlights include hipped-pitch roof and frame. Honey art glass with Weathered Bronze finish. Die-cast aluminum construction.

FINISH

● Weathered Bronze - 46

PATH LIGHT

P5272-46 Weathered Bronze
Low voltage path light.
(Requires transformer).
5-1/2" W., 7-1/2" ht.
Extends 6-1/2".
One 18w T5 wedge base lamp
(included).



POST LANTERN

P5428-46 Weathered Bronze
10" W., 18-1/8" ht.
Fits 3" post (order separately).
One medium base lamp,
150w max.

HANGING LANTERN

P5528-46 Weathered Bronze
10" W., 15-1/4" ht.
Overall ht. w/chain 52"; wire 10'.
One medium base lamp,
150w max.

MEDIUM WALL LANTERN

P5628-46 Weathered Bronze
6-5/8" W., 10-1/2" ht.
Extends 7-1/2". H/CTR 2-1/4".
One medium base lamp,
100w max.

LARGE WALL LANTERN

P5629-46 Weathered Bronze
10" W., 15-1/4" ht.
Extends 10-3/4". H/CTR 10".
One medium base lamp,
150w max.

P5628-46



P5528-46



P5629-46



P5272-46



P5428-46





Modern forms and layered glass. Etched opal glass within seeded glass shade, offers design flexibility for exterior settings and in unexpected interior applications. Steel construction with a powder coat finish.

FINISH

- Black - 31

SMALL WALL LANTERN

P6038-31 Black
 5-3/4" W., 9-7/8" ht.
 Extends 7-1/4". H/CTR 5-1/4".
 One medium base lamp,
 100w max.

MEDIUM WALL LANTERN

P6039-31 Black
 7-7/8" W., 13-1/2" ht.
 Extends 9-3/8". H/CTR 7-1/2".
 One medium base lamp,
 100w max.

POST LANTERN

P6420-31 Black
 7-7/8" W., 21-5/8" ht.
 Fits 3" post (order separately).
 One medium base lamp,
 100w max.

HANGING LANTERN

P6520-31 Black
 7-7/8" dia., 15-3/8" ht.
 Overall ht. w/chain 90"; wire 15'.
 One medium base lamp,
 100w max.

GREETINGS



Greet guests with an architectural inspired frame. Modern drum profile and etched glass shades. Powder coat Antique Bronze finish. Aluminum and steel construction.

FINISH

● Antique Bronze - 20

POST LANTERN

P5449-20 Antique Bronze
9-1/2" dia., 23-3/4" ht.
Fits 3" post (order separately).
One medium base lamp,
100w max.

HANGING LANTERN

P5549-20 Antique Bronze
9-1/2" dia., 21-3/4" ht.
Overall ht w/chain 96"; wire 10'.
One medium base lamp,
100w max.

SMALL WALL LANTERN

P5631-20 Antique Bronze
5-3/4" W., 12-3/4" ht.
Extends 8". H/CTR 6-1/2".
One medium base lamp,
100w max.

MEDIUM WALL LANTERN

P5719-20 Antique Bronze
7-5/8" W., 16-5/8" ht.
Extends 10". H/CTR 9-1/8".
One medium base lamp,
100w max.

LARGE WALL LANTERN

P5728-20 Antique Bronze
9 1/2" W., 20-3/4" ht.
Extends 12-3/8". H/CTR 11-1/8".
One medium base lamp,
100w max.



P5631-20



P5719-20



P5728-20



P5549-20



P5449-20



Rediscover antique nautical lanterns with etched glass diffuser surrounded by water glass gallery. Aluminum and steel construction. Antique Bronze powder coat finish.

FINISH

- Antique Bronze - 20

FLUSH MOUNT

P3942-20 Antique Bronze
15" dia., 7-3/8" ht.
Two medium base lamps,
each 60w max.



POST LANTERN

P5499-20 Antique Bronze
8-3/4" dia., 14-1/2" ht.
Fits 3" post (order separately).
One medium base
lamp, 100w max.

HANGING LANTERN

P5589-20 Antique Bronze
8-3/4" dia., 12-3/4" ht.
Overall ht w/chain 87"; wire 10'.
One medium base lamp,
100w max.

MEDIUM WALL LANTERN

P5849-20 Antique Bronze
8-3/4" W., 10-1/4" ht.
Extends 10-3/8". H/CTR 5-1/4".
One medium base lamp,
100w max.



LARGE WALL LANTERN

P5851-20 Antique Bronze
11-5/8" W., 13-5/8" ht.
Extends 13-3/8". H/CTR 6-7/8".
One medium base lamp,
100w max.

FAIRVIEW

Explore the great outdoors with classic details. Softly etched glass and a Powder Coat Textured finish on aluminum frame.

FINISH

- Black - 31

POST LANTERN

P5402-31 Textured Black
10-1/2" dia., 18-1/4" ht.
Fits 3" post (order separately).
One medium base lamp,
100w max.

SMALL WALL LANTERN

P5775-31 Textured Black
6-1/2" W., 11-3/4" ht.
Extends 8-1/2". H/CTR 3-3/4".
One medium base lamp,
75w max.

MEDIUM WALL LANTERN

P5778-31 Textured Black
8-3/8" W., 14-1/2" ht.
Extends 11-1/4". H/CTR 10".
One medium base lamp,
100w max.

LARGE WALL LANTERN

P5780-31 Textured Black
10-1/2" W., 17" ht.
Extends 12-1/4". H/CTR 12-1/2".
One medium base lamp,
100w max.



P5775-31



P5402-31



P5778-31



P5780-31



The Format collection is comprised of an oval form factor with grid overlay. Etched glass shades. Cast aluminum with a powder coat finish.

FINISH

- Black - 31

SMALL WALL LANTERN

P6062-31 Black
 5-7/8" W., 7-5/8" ht.
 Extends 4-7/8". H/CTR 2-3/4".
 One medium base lamp,
 100w max.

MEDIUM WALL LANTERN

P6063-31 Black
 7-3/8" W., 11-5/8" ht.
 Extends 6". H/CTR 3-1/2".
 One medium base lamp,
 100w max.

LARGE WALL LANTERN

P6064-31 Black
 9-1/2" W., 16-1/8" ht.
 Extends 7-1/2". H/CTR 4-5/8".
 One medium base lamp,
 100w max.

POST LANTERN

P6428-31 Black
 9-1/2" W., 17-1/8" ht.
 Fits 3" post (order separately).
 One medium base lamp,
 100w max.

SMALL HANGING LANTERN

P6528-31 Black *
 5-7/8" W., 7-3/8" ht.
 Overall ht. w/chain 72-5/8"; wire 15'.
 One medium base lamp,
 100w max.

PIER 33

Outdoor hanging and wall lanterns from the Pier 33 collection feature coastal undertones and a design reminiscent of industrial spaces. LED and incandescent options are comprised of a die-cast frame. Clear seeded glass complements a Black finish.

FINISH

- Black - 031

HANGING LANTERN

P550005-031 Black
8-1/8" dia., 13-1/4" ht.
Overall ht. w/chain 79-1/2"; wire 10'.
One medium base lamp,
100w max.

LED FEATURES

- 120v AC, replaceable module
- 9w 624 lumens, 66.1 lumens/watt
- 3000K color temperature; 90 CRI
- Dimmable to 10% brightness with ELV type dimmers

LED HANGING LANTERN

P550010-031-30 Black
8-1/8" dia., 13-1/4" ht.
Overall ht. 79-1/2". wire 10".
One 9w LED module included.



WALL-LANTERN

P560024-031 Black
8-1/8" W., 13" ht.
Extends 9". H/CTR 3-1/4".
One medium base lamp,
100w max.

LED WALL LANTERN

P560034-031-30 Black
8-1/8" dia., 13" ht.
Extends 9". H/CTR 3-1/4".
One 9w LED module included.



P550005-031



P550010-031-30



P560024-31



P560034-031-30

ELLIPSES

An LED wall lantern featuring an etched white pillar candle inside a clear globe glass design. A replaceable AC LED module sits at the base of the Black frame and illuminates upward for a striking visual effect.

FINISH

- Black - 031

LED WALL LANTERN

P560000-031-30 Black
8" W., 15-1/2" ht.
Extends 11-7/8". H/CTR 7-3/4".
One 9w LED module included.



LED FEATURES

- 120v AC, replaceable module
- 9w 670 lumens, 71.1 lumens/watt
- 3000K color temperature; 90 CRI
- Dimmable to 10% brightness with ELV type dimmers



P560000-031-30

LED Z-1010



P560029-028-30



P560029-031-30



P560029-129-30

A modern outdoor sconce with an open linear frame and seeded glass diffuser. Finished in Black, Satin White and Architectural Bronze.

FINISHES

- Satin White - 028
- Black - 031
- Architectural Bronze - 129

LED WALL LANTERN

P560029-028-30 Bright White

P560029-031-30 Black

P560029-129-30 Architectural Bronze

7-1/2" W., 16" ht.

Extends 4". H/CTR 4-1/4".

One 9w LED module included.

624 source lumens, 66 lumens/watt.



PROGRESS **LED**

LED Z-1020



P560030-031-30



P560030-129-30

A modern outdoor sconce with white glass shade is suspended in a curved frame that serves as a reflector when illuminated. Finished in Black or Architectural Bronze.

FINISHES

- Black - 031
- Architectural Bronze - 129

LED WALL LANTERN

P560030-031-30 Black

P560030-129-30 Architectural Bronze

7-1/2" W., 13-1/2" ht.

Extends 4-3/4". H/CTR 11-1/8".

One 9w LED module included.

670 source lumens, 71 lumens/watt.



PROGRESS **LED**

LED FEATURES

- 120v AC, replaceable module
- 3000K color temperature; 90 CRI
- Dimmable to 10% brightness with ELV type dimmers

JACK

Rectilinear design. Antique Bronze finish with etched amber flax glass. Black finish with etched white glass. Steel construction.

FINISHES

- Antique Bronze - 20
- Black - 31

SMALL WALL LANTERN

P5948-20 Antique Bronze

P5948-31 Black

6" W., 13-5/8" ht.

Extends 6-1/4". H/CTR 5-1/4".

One medium base lamp,

100w max.

MEDIUM WALL LANTERN

P5949-20 Antique Bronze

P5949-31 Black

8" W., 15-1/4" ht.

Extends 6-1/4". H/CTR 5-7/8".

One medium base lamp,

100w max.



P5948-20



P5949-20



P5948-31



P5949-31

PEEK-A-BOO

Etched glass shade "peeks through" arched frame. Clean, contemporary wall lanterns in steel construction with antique bronze powder coat finish.

FINISH

- Antique Bronze - 20

MEDIUM WALL LANTERN

P6602-20 Antique Bronze

5-1/2" W., 13" ht.

Extends 3-1/4". H/CTR 7-1/4".

One candelabra base lamp,

60w max.

LARGE WALL LANTERN

P6603-20 Antique Bronze

5-1/2" W., 17-1/8" ht.

Extends 3-1/4". H/CTR 10-3/4".

One medium base T10 lamp,

60w max.



P6602-20



P6603-20

PARKER

White acrylic diffuser. Can be used indoors and outdoors. Remove top and bottom end caps for indoor use. die-cast aluminum construction with powder coat finish.



P5914-16



P5914-20



P5915-16



P5915-20

MEDIUM WALL LANTERN

P5914-16 Satin Aluminum

P5914-20 Antique Bronze

White acrylic diffuser.

5-3/8" W., 10-1/4" ht.

Extends 4".

One GU24 CFL lamp,

26w max.

ADA



FINISHES

● Satin Aluminum - 16

● Antique Bronze - 20

LARGE WALL LANTERN

P5915-16 Satin Aluminum

P5915-20 Antique Bronze

White acrylic diffuser.

5-3/8" W., 16-7/8" ht.

Extends 4".

Two GU24 CFL lamps,

each 26w max.

ADA



ANSON

Enjoy a sleek and modern design. White geometric enclosed diffuser framed in Bronze or Brushed Nickel shield. For Indoor or outdoor use.



P5736-09



P5736-129

WALL LANTERN

P5736-09 Brushed Nickel

P5736-129 Architectural Bronze

Can be used indoors or outdoors.

9-1/8" W., 10-1/4" ht.

Extends 3-3/4". H/CTR 5-5/8".

One GU24 CFL lamp, 18w max.



ADA

FINISHES

● Brushed Nickel - 09

● Architectural Bronze - 129



P560001-135-30



P560001-129-30

ANSON LED

One-light ADA wall lantern with polycarbonate diffuser and stainless steel frame. 3000 K, 90+CRI, 1452 lumens.

WALL LANTERN

P560001-135-30 Stainless Steel

P560001-129-30 Architectural

Bronze

10" W., 3" ht.

One 3000K 17w LED

module included.



ADA

FINISHES

● Stainless Steel - 135

● Architectural Bronze - 129

VALERA

Transform outdoor settings with a bold, straightforward style. Double linear details finished in Brushed Nickel or Antique Bronze over a white acrylic diffuser. Die-cast aluminum construction.

FINISHES

- Brushed Nickel - 09
- Antique Bronze - 20

SMALL WALL LANTERN

P5800-09 Brushed Nickel

P5800-20 Antique Bronze

5-5/8" W., 8" ht.

Extends 4". H/CTR 4".

One GU24 CFL lamp,

18w max.

ADA



MEDIUM WALL LANTERN

P5801-09 Brushed Nickel

P5801-20 Antique Bronze

8-5/8" W., 11" ht.

Extends 4". H/CTR 5-1/2".

One GU24 CFL lamp,

26w max.

ADA



LARGE WALL LANTERN

P5806-09 Brushed Nickel

P5806-20 Antique Bronze

5-5/8" W., 16" ht.

Extends 4". H/CTR 8".

Two GU24 CFL lamps,

each 18w max.

ADA



P5800-09



P5800-20



P5801-09



P5801-20



P5806-09



P5806-20



P5800-0930K9



P5800-12930K9



P5801-0930K9



P5801-12930K9



P5806-0930K9



P5806-12930K9

FINISHES

- Brushed Nickel - 09
- Architectural Bronze - 129

LED WALL LANTERN

P5800-0930K9 Brushed Nickel

P5800-12930K9 Architectural Bronze

5-5/8" W., 8" ht.

Extends 4". H/CTR 4".

One 9w LED module included.

623 lumens per module, 90 CRI.

ADA



LED WALL LANTERN

P5801-0930K9 Brushed Nickel

P5801-12930K9 Architectural Bronze

8-5/8" W., 11" ht.

Extends 4". H/CTR 5-1/2".

One 17w LED module included.

1211 lumens per module, 90 CRI.

ADA



LED WALL LANTERN

P5806-0930K9 Brushed Nickel

P5806-12930K9 Architectural Bronze

5-5/8" W., 16" ht.

Extends 4". H/CTR 8".

Two 9w LED modules included.

623 lumens per module, 90 CRI.

ADA



LED FEATURES

- 120V AC, replaceable module
- 9w: 623 lumens, 69.2 lumens/watt
- 17w: 1211 lumens, 71.2 lumens/watt
- 3000K color temperature; 90+ CRI
- TM-21 60,000 hr. life
- Dimmable to 10% brightness with many ELV type dimmers



CORNICE

OUTDOOR

Modern geometric outdoor LED sconces are designed to complement a range of residential and commercial architectural styles. ADA compliant. Available in Black, Antique Bronze and Metallic Gray finishes.

FINISHES

- Antique Bronze - 20
- Black - 31
- Metallic Gray - 82

LED OUTDOOR WALL SCONCE

P5634-2030K9 Antique Bronze

P5634-3130K9 Black

P5634-8230K9 Metallic Gray

5-1/4" W., 4-3/4" ht.

Extends 4". H/CTR 2-3/8".

One 9w LED module included.

ADA



LED OUTDOOR WALL SCONCE

P5635-2030K9 Antique Bronze

P5635-3130K9 Black

P5635-8230K9 Metallic Gray

6-1/8" W., 5" ht.

Extends 4". H/CTR 2-3/8".

One 9w LED module included.

ADA



LED FEATURES

- 120V AC Replaceable LED module
- 623 lumens, 69.2 lumens/watt
- 3000K color temperature; 90+ CRI
- TM-21 60,000 hr. life

PROGRESS **LED**



P5634-2030K9



P5635-2030K9



P5634-3130K9



P5635-3130K9



P5634-8230K9



P5635-8230K9

BELL

Featuring nautical undertones, the Bell outdoor collection offers cage lights reminiscent of industrial architecture. Ideal for use in both interior and exterior settings, this LED fixture is available in convertible ceiling/pendant and wall mount options.

FINISHES

- Antique Bronze - 20
- Textured Graphite -136

SMALL WALL LANTERN

P5676-2030K9 Antique Bronze

P5676-13630K9 Textured Graphite

5-1/2" W., 10-5/8" ht.

Extends 7-3/8". H/CTR 3".

One 9w LED module included.



CEILING/PENDANT

P6536-2030K9 Antique Bronze

P6536-13630K9 Textured Graphite

6-5/8" dia., 11-3/8" ht.

Overall ht. w/chain 77"; wire 12'.

One 9w LED module included.



LED FEATURES

- 120V AC Replaceable LED module
- 623 lumens, 69.2 lumens/watt
- 3000K color temperature; 90+ CRI
- TM-21 60,000 hr. life

PROGRESS **LED**



P6536-2030K9
Shown as ceiling mount



P6536-13630K9
Shown as ceiling mount



P5676-2030K9



P5676-13630K9

DISTRICT



District's metal shade offers an industrial-inspired design. Available in both incandescent and LED versions, the versatile vintage form can be used in indoor and outdoor applications. Dark sky compliant.

FINISHES

- Antique Bronze - 20
- Metallic Gray -82

MEDIUM HANGING LANTERN

P5535-20 Antique Bronze

P5535-82 Metallic Gray

8" dia., 6-1/4" ht.

Overall ht. w/cord 130"; wire 12'.

One medium base lamp,

100w max.

LARGE HANGING LANTERN

P5551-20 Antique Bronze

P5551-82 Metallic Gray

12" dia., 8-1/4" ht.

Overall ht. w/cord 130"; wire 12'.

One medium base lamp,

100w max.

MEDIUM WALL LANTERN

P5622-20 Antique Bronze

P5622-82 Metallic Gray

8" W., 8-1/4" ht.

Extends 10-1/4". H/CTR 4-1/8".

One medium base lamp,

100w max.

LARGE WALL LANTERN

P5623-20 Antique Bronze

P5623-82 Metallic Gray

12" W., 10-1/2" ht.

Extends 13-1/4". H/CTR 5".

One medium base lamp,

100w max.



P5535-20



P5535-82



P5551-20



P5551-82



P5622-20



P5622-82



P5623-20



P5623-82



P5551-2030K9



P5551-8230K9



P5535-2030K9



P5535-8230K9



P5622-2030K9



P5622-8230K9



P5623-2030K9



P5623-8230K9

FINISHES

- Antique Bronze - 20
- Metallic Gray - 82

LARGE HANGING LANTERN

P5551-2030K9 Antique Bronze

P5551-8230K9 Metallic Gray

12" dia., 8-1/4" ht.

Overall ht. w/cord 130"; wire 12'.

One 9w LED module included.



MEDIUM HANGING LANTERN

P5535-2030K9 Antique Bronze

P5535-8230K9 Metallic Gray

8" dia., 6-1/4" ht.

Overall ht. w/cord 130"; wire 12'.

One 9w LED module included.



MEDIUM WALL LANTERN

P5622-2030K9 Antique Bronze

P5622-8230K9 Metallic Gray

8" W., 8-1/4" ht.

Extends 10-1/4". H/CTR 4-1/8".

One 9w LED module included.



LARGE WALL LANTERN

P5623-2030K9 Antique Bronze

P5623-8230K9 Metallic Gray

12" W., 10-1/2" ht.

Extends 13-1/4". H/CTR 5".

One 9w LED module included.




LED FEATURES

- 120V AC Replaceable LED module
- 623 lumens, 69.2 lumens/watt
- 3000K color temperature; 90+ CRI
- TM-21 60,000 hr. life
- Dimmable to 10% with many ELV type dimmers



EAST HAVEN



East Haven offers contemporary styling to complement a variety of home styles. A Black or Antique Bronze die-cast aluminum frame cradles a seeded glass shade.

FINISHES

- Antique Bronze - 20
- Black - 31

SMALL WALL LANTERN

P6073-20 Antique Bronze
P6073-31 Black
 5-3/4" W., 10-3/8" ht.
 Extends 7". H/CTR 5-3/4".
 One medium base lamp,
 100w max.

MEDIUM WALL LANTERN

P6074-20 Antique Bronze
P6074-31 Black
 7-1/2" W., 12-3/4" ht.
 Extends 9-1/2". H/CTR 7-1/4".
 One medium base lamp,
 100w max.

LARGE WALL LANTERN

P6075-20 Antique Bronze
P6075-31 Black
 9-1/2" W., 15-1/8" ht.
 Extends 11-1/2". H/CTR 9-3/4".
 One medium base lamp,
 100w max.

POST LANTERN

P6425-20 Antique Bronze
P6425-31 Black
 7-1/2" dia., 15" ht.
 Fits 3" post (order separately).
 One medium base lamp,
 100w max.

HANGING LANTERN

P6525-20 Antique Bronze
P6525-31 Black
 7-1/2" dia., 13-3/8" ht.
 Overall ht. w/chain 90"; wire 15'.
 One medium base lamp,
 100w max.



P6525-20



P6525-31



P6073-20



P6073-31



P6074-20



P6074-31



P6425-20



P6425-31



P6075-20



P6075-31

EAST HAVEN LED



P6530-2030K9



P6530-3130K9



P6077-2030K9



P6077-3130K9



P6078-2030K9



P6078-3130K9



P6079-2030K9



P6079-3130K9



P6430-2030K9



P6430-3130K9

East Haven offers contemporary styling to complement today's home styles. A Black or Antique Bronze frame cradles a seeded glass shade.

FINISHES

- Antique Bronze - 20
- Black - 31

SMALL WALL LANTERN

P6077-2030K9 Antique Bronze

P6077-3130K9 Black

5-3/4" W., 7-7/8" ht.

Extends 7-1/2". H/CTR 4-3/4".

One 9w LED module included.



MEDIUM WALL LANTERN

P6078-2030K9 Antique Bronze

P6078-3130K9 Black

7-1/2" W., 9-3/4" ht.

Extends 9-1/8". H/CTR 4-3/4".

One 9w LED module included.



LARGE WALL LANTERN

P6079-2030K9 Antique Bronze

P6079-3130K9 Black

9-1/2" W., 12" ht.

Extends 11-1/8". H/CTR 4-3/4".

One 17w LED module included.



POST LANTERN

P6430-2030K9 Antique Bronze

P6430-3130K9 Black

7-1/2" dia., 15" ht.

Fits 3" post (order separately).

One 9w LED module included.



HANGING LANTERN

P6530-2030K9 Antique Bronze

P6530-3130K9 Black

7-1/2" dia., 10-3/8" ht.

Overall ht. w/chain 86-1/2";

wire 15'.

One 9w LED

module included.



LED FEATURES

- 120V AC
- Replaceable LED module
- 9w: 623 lumens, 69.2 lumens/watt
- 17w: 1211 lumens, 71.2 lumens/watt
- 3000K color temperature; 90+ CRI
- TM-21 60,000 hr. life
- Dimmable to 10% with many ELV type dimmers

PROGRESS **LED**

WESTPORT



Classic styling with detailed touches. Clear seeded glass with die-cast aluminum frames and durable powder coat finish.

FINISHES

- Antique Bronze - 20
- White - 30
- Black - 31

FLUSH MOUNT

P3883-20 Antique Bronze
P3883-31 Black
 9" dia., 10-1/4" ht.
 One medium base lamp,
 100w max.

POST LANTERN

P5445-20 Antique Bronze
P5445-30 White
P5445-31 Black
 9" dia., 16-3/8" ht.
 Fits 3" post (order separately).
 One medium base lamp,
 100w max.

HANGING LANTERN

P5530-20 Antique Bronze
P5530-31 Black
 9" dia., 14-5/8" ht.
 Overall ht. w/chain 90", wire 15'.
 One medium base lamp,
 100w max.

SMALL WALL LANTERN

P5862-20 Antique Bronze
P5862-30 White
P5862-31 Black
 6-7/8" W., 12-5/8" ht.
 Extends 8-3/8". H/CTR 3-1/8".
 One medium base lamp,
 60w max.



P5862-20



P3883-20



P3883-31



P5530-20



P5530-31

LARGE WALL LANTERN

P5864-20 Antique Bronze
P5864-31 Black
 11" W., 19-1/2" ht;
 Extends 12-7/8". H/CTR 4-5/8".
 Two candelabra base lamps,
 each 60w max.



P5863-20



P5863-31

MEDIUM WALL LANTERN

P5863-20 Antique Bronze
P5863-30 White
P5863-31 Black
 9" W., 15-7/8" ht.
 Extends 10-3/8". H/CTR 3-1/4".
 One medium base lamp,
 100w max.



P5445-20



P5445-31



Shown: P5863-31 lantern (Image: Toll Brothers)



P5864-20



P5864-31



P5862-31



P5862-30



P5863-30



P5445-30

WESTPORT GU24



Add a touch of rustic appeal with beaded detailing. Etched seeded glass with die-cast aluminum frames with durable powder coat finish.

FINISHES

- Antique Bronze - 20
- Black - 31

FLUSH MOUNT

P3883-20WB Antique Bronze

P3883-31WB Black

9" dia., 10-1/2" ht.

One 13w GU24 CFL lamp,
(included).



SMALL WALL LANTERN

P5862-20WB Antique Bronze

P5862-31WB Black

6-7/8" W., 12-3/4" ht.

Extends 8-3/8". H/CTR 3-1/4".

One 13w GU24 CFL lamp,
(included).



MEDIUM WALL LANTERN

P5863-20WB Antique Bronze

P5863-31WB Black

9" W., 16" ht.

Extends 10-3/8". H/CTR 3-1/2".

One 13w GU24 CFL lamp,
(included).



LARGE WALL LANTERN

P5864-20WB Antique Bronze

P5864-31WB Black

11" W., 19-1/2" ht.

Extends 12-7/8". H/CTR 4-5/8".

One 18w GU24 CFL lamp,
(included)



P3883-20WB



P3883-31WB



P5862-20WB



P5862-31WB



P5863-20WB



P5863-31WB



P5864-20WB



P5864-31WB

WESTPORT LED

Westport LED offers traditional styling to complement a variety of home décor options. A durable, die-cast aluminum frame cradles a softly diffused, seeded glass shade.



P3883-2030K9



P3883-3130K9



P5862-2030K9



P5862-3130K9
P5861-3130K9



P5863-2030K9



P5863-3130K9



P5864-2030K9



P5864-3130K9



P5445-2030K9



P5445-3130K9

FINISHES

- Antique Bronze - 20
- Black - 31

FLUSH MOUNT

P3883-2030K9 Antique Bronze
P3883-3130K9 Black
 9" dia., 7-1/4" ht.
 One 17w LED module included.



POST LANTERN

P5445-2030K9 Antique Bronze
P5445-3130K9 Black
 9" dia., 16-3/8" ht.
 Fits 3" post (order separately).
 One 9w LED module included.



SMALL WALL LANTERN

P5861-3130K9 Black
 Meets CA Title 24 Standards (JA8)
 6-7/8" W., 10-1/4" ht.
 Extends 8-3/8". H/CTR 3-1/8".
 One 9w LED module included.



SMALL WALL LANTERN

P5862-2030K9 Antique Bronze
P5862-3130K9 Black
 6-7/8" W., 10-1/4" ht.
 Extends 8-3/8". H/CTR 3-1/8".
 One 9w LED module included.



MEDIUM WALL LANTERN

P5863-2030K9
 Antique Bronze
P5863-3130K9 Black
 9" W., 12-7/8" ht.
 Extends 10-3/8". H/CTR 3-3/4".
 One 9w LED module included.



LARGE WALL LANTERN

P5864-2030K9
 Antique Bronze
P5864-3130K9 Black
 11" W., 15-3/8" ht.
 Extends 12-7/8". H/CTR 4".
 One 17w LED module included.




LED FEATURES

- 120v AC, replaceable module
- 9w: 623 lumens, 69.2 lumens/watt
 17w: 1211 lumens, 71.2 lumens/watt
- 3000K color temperature; 90 CRI
- Dimmable to 10% brightness with ELV type dimmers

PROGRESS **LED**

BURLINGTON



The Burlington collection features all aluminum construction, weather-resistant performance with clear beveled glass panels.

FINISHES

- Brushed Nickel - 09
- Antique Bronze - 20

POST LANTERN

P6437-09 Brushed Nickel
P6437-20 Antique Bronze
 9" sq., 18-3/8" ht.
 Fits 3" post (order separately).
 Two candelabra base lamps,
 each 60w max.



P6437-09

HANGING LANTERN

P6537-09 Brushed Nickel
P6537-20 Antique Bronze
 9" sq., 15-3/4" ht.
 Overall ht. w/chain 91"; wire 10'.
 Two candelabra base lamps,
 each 60w max.



P6616-09



P6616-20

SMALL WALL LANTERN

P6615-09 Brushed Nickel
P6615-20 Antique Bronze
 7" W., 12-7/8" ht.
 Extends 7-3/4". H/CTR 4-1/8".
 One medium base lamp,
 100w max.



P6615-09



P6615-20

MEDIUM WALL LANTERN

P6616-09 Brushed Nickel
P6616-20 Antique Bronze
 9" W., 18-3/4" ht.
 Extends 9-3/4". H/CTR 7-5/8".
 Two candelabra base lamps,
 each 60w max.



P6437-20



P6617-09



P6617-20

LARGE WALL LANTERN

P6617-09 Brushed Nickel
P6617-20 Antique Bronze
 11" W., 21-7/8" ht.
 Extends 11-3/4". H/CTR 8-5/8".
 Three candelabra base lamps,
 each 60w max.



P6537-09



P6537-20

NEW HAVEN



P6533-31



P6533-09



P6610-31



P6610-09



P6611-31



P6611-09



P6612-31



P6612-09



A Brushed Nickel or Black finish complements clear beveled glass in the New Haven outdoor lantern collection.

FINISHES

- Brushed Nickel - 09
- Black - 31

POST LANTERN

P6433-09 Brushed Nickel

P6433-31 Black

11" dia., 23" ht.

Fits 3" post (order separately).
Three candelabra base lamps,
each 60w max.



P6433-09

HANGING LANTERN

P6533-09 Brushed Nickel

P6533-31 Black

11" dia., 19-3/4" ht.

Overall ht. w/chain 95"; wire 10'.
Three candelabra base lamps,
each 60w max.

SMALL WALL LANTERN

P6610-09 Brushed Nickel

P6610-31 Black

7-5/8" W., 14-7/8" ht.

Extends 7-3/8". H/CTR 5-1/2".

One medium base lamp,
100w max.

MEDIUM WALL LANTERN

P6611-09 Brushed Nickel

P6611-31 Black

9" W., 18-1/8" ht.

Extends 8-5/8". H/CTR 8-1/2".

One candelabra base lamp,
100w max.

LARGE WALL LANTERN

P6612-09 Brushed Nickel

P6612-31 Black

11" W., 21-7/8" ht.

Extends 10-3/8". H/CTR 8-5/8".

Three candelabra base lamps,
each 60w max.



P6433-31

ROMAN COACH



The rich weathered finish is complemented by clear seeded glass panes. A great choice for low maintenance and years of enjoyment. Comes in Antique Bronze and Black finishes.

FINISHES

- Antique Bronze - 20
- Black - 31



P5565-31



P5565-20

P5773-20
shown with tailP5773-20
shown without tail

PRODUCT NO.	FINISH	DESCRIPTION	SIZE	LAMP(S)
P5475-20	Antique Bronze	Post lantern	7" W., 15-3/4" ht. Fits 3" post (order separately).	1 medium base, 100w max.
P5565-20 P5565-31	Antique Bronze Black	Hanging lantern. Chain and ceiling mounts included.	7" dia., 13" ht. Overall ht. w/chain 36"; wire 10'. Ceiling mount ht. 12-3/4".	1 medium base, 100w max.
P5762-20 P5762-31	Antique Bronze Black	Small wall lantern	6" W., 9-3/4" ht. Extends 6-1/2". H/CTR 3-1/2".	1 medium base, 100w max.
P5765-20 P5765-31	Antique Bronze Black	Medium wall lantern	7" W., 15-1/4" ht. Extends 7-1/4". H/CTR 6-7/8".	1 medium base, 100w max.
P5767-20 P5767-31	Antique Bronze Black	Medium wall lantern. Can be used with or without tail.	7" W., 26-3/8" ht. w/tail. 19-1/4" ht. w/o tail. Extends 7". H/CTR 16-1/4".	1 medium base, 100w max.
P5773-20	Antique Bronze	Small wall lantern. Can be used with or without tail	5-3/4" W., 18-1/4" ht. w/tail. 13-1/2" ht. w/o tail. Extends 5-3/4". H/CTR 7-1/4".	1 medium base, 100w max.
P5777-20	Antique Bronze	Medium wall lantern	7" W., 12-1/2" ht. Extends 7-1/4". H/CTR 4".	1 medium base, 100w max.
P6019-20 P6019-31	Antique Bronze Black	Flush mount	11" W., 6-3/8" ht.	2 medium base, each 60w max.
P6417-20 P6417-31	Antique Bronze Black	Post lantern	9-1/2" W., 22-1/2" ht. Fits 3" post (order separately).	1 medium base, 100w max.



P5777-20



P5475-20



P6019-20



P6019-31



P5767-20
shown without tail



P5762-20



P5762-31



P5767-20
shown with tail



P5765-20



P5765-31



P6417-20



P6417-31






P5767-31
(shown with tail)

ROMAN COACH CFL

A timeless style with environmentally friendly benefits. Etched seeded glass in Brushed Nickel, Antique Bronze or Black finishes. Solid brass and aluminum construction.

FINISHES

- Brushed Nickel - 09
- Antique Bronze - 20

PRODUCT NO.	FINISH	DESCRIPTION	SIZE	LAMP(S)	
P5766-09	Brushed Nickel	One-light wall lantern	6" W., 9-7/8" ht. Extends 7". H/CTR 3-1/2".	1 26w GU24 CFL lamp 26w max.	
P5766-20	Antique Bronze				
P5770-09	Brushed Nickel	One-light wall lantern	7" W., 15-3/8" ht. Extends 7-1/4". H/CTR 6-7/8".	1 26w GU24 CFL lamp 26w max.	
P5770-20	Antique Bronze				
P5772-09	Brushed Nickel	One-light wall lantern*	7" W., 26-3/8" ht. w/tail. 19-1/4" ht. w/o tail. Extends 6-7/8". H/CTR 16-1/4".	1 26w GU24 CFL lamp 26w max.	
P5772-20	Antique Bronze				

*Can be installed with or without tail.



P5766-09



P5766-20



P5770-09



P5770-20



P5772-09
shown without tail





P5772-09
shown with tail



P5772-20
shown with tail

ROMAN COACH CFL

PRODUCT NO.	FINISH	DESCRIPTION	SIZE	LAMP(S)	
P5985-09WB	Brushed Nickel	One-light wall lantern	4-5/8" W., 10" ht. Extends 6-1/8". H/CTR 2-3/4".	1 26w GU24 CFL lamp (included)	
P5985-20WB	Antique Bronze				
P5985-31WB	Black				
P5986-09	Brushed Nickel	One-light wall lantern	4-5/8" W., 8-1/2" ht. Extends 6-1/8". H/CTR 2-3/4".	1 13w GU24 CFL lamp	
P5986-20	Antique Bronze				
P5986-31	Black				

FINISHES

- Brushed Nickel - 09
- Antique Bronze - 20
- Black - 31



P5986-09



P5986-20



P5985-09WB



P5985-20WB



P5985-31WB



MILFORD LED

Etched glass surrounded by a die-cast aluminum frame, ideal for indoor and outdoor application.

FINISHES

- Antique Bronze - 20
- Black - 31



PRODUCT NO.	FINISH	DESCRIPTION	SIZE	LAMP(S)
P3665-2030K9 P3665-3130K9	Antique Bronze Black	One-light flush mount	8-5/8" dia., 4-1/8" ht.	1 17w LED module included 
P3673-2030K9 P3673-3130K9	Antique Bronze Black	One-light flush mount	10-5/8" dia., 4-7/8" ht.	1 17w LED module included 



P3665-2030K9



P3665-3130K9



P3673-2030K9




P3673-3130K9

MILFORD CFL

Durable aluminum construction with powder coat finish and white matte acrylic diffuser.

FINISHES

- Antique Bronze - 20
- Black - 31

PRODUCT NO.	FINISH	SIZE	LAMP
P5821-20 P5821-31	Antique Bronze Black	5-3/4" W., 8-3/4" ht. Extends 4-5/8". H/CTR 5-1/8"	1 13w GU24 CFL 



P5821-20



P5821-31

BRASSGUARD® LANTERNS

Unique, clear lacquer applied for long-lasting finish. All-brass construction includes protective gasket to reduce staining on siding. Black fixtures utilize aluminum construction with clear lacquer coating.

FINISHES

- Brushed Nickel - 09
- Polished Brass - 10
- Black - 31

LARGE LANTERNS

PRODUCT NO.	FINISH	DESCRIPTION	SIZE	LAMP(S)
P5432-10 P5432-31	Polished Solid Brass Black	Post lantern	9-1/2" dia., 21" ht. Fits 3" post (order separately).	3 candelabra base, each 60w max.
P5730-10	Polished Solid Brass	Wall lantern	9-1/2" W., 26" ht. Extends 9-1/2". H/CTR 20-1/4".	3 candelabra base, each 60w max.
P5731-31	Black	Wall lantern	9-1/2" W., 35" ht. Extends 9-1/2". H/CTR 20-1/2".	3 candelabra base, each 60w max.



P5730-10



P5731-31



P5432-10



P5432-31

MEDIUM LANTERNS

PRODUCT NO.	FINISH	DESCRIPTION	SIZE	LAMP(S)
P5430-10	Polished Solid Brass	One-light post Fits 3" post (order separately).	7" dia., 17" ht.	1 medium base, 100w max.
P5831-31	Black	One-light wall lantern	7" W., 29" ht. Extends 6-3/4". H/CTR 15-3/8".	1 medium base, 100w max.
P5832-10	Polished Solid Brass	One-light wall lantern	7" W., 14-1/4" ht. Extends 7". H/CTR 5-3/8".	1 medium base, 100w max.
P5834-10	Polished Solid Brass	One-light hanging lantern. Chain and ceiling mounts both included.	7" dia., 10" ht. Overall ht. w/chain 39-1/2"; wire 10'.	1 medium base, 100w max.



P5834-10
chain mount



P5834-10
ceiling mount



P5832-10



P5831-31



P5430-10

SMALL LANTERNS

PRODUCT NO.	FINISH	DESCRIPTION	SIZE	LAMP(S)
P5756-09	Brushed Nickel	One-light wall lantern. Open bottom.	5-1/2" W., 10-1/4" ht. Extends 5-3/4". H/CTR 3-3/4".	1 medium base, 100w max.
P5756-10	Polished Solid Brass			
P5756-31	Black			
P5758-31	Black	One-light wall lantern	5-1/2" W., 18-3/4" ht. Extends 5-5/8". H/CTR 7-1/4".	1 medium base, 100w max.
P5846-31	Black	One-light wall lantern	5-1/4" W., 14-3/4" ht. Extends 6". H/CTR 8-3/8".	1 medium base, 60w max.



P5756-09



P5756-10



P5756-31



P5758-31



P5846-31

COACH LANTERNS

Square fixture with clear flat glass.

PRODUCT NO.	FINISH	DESCRIPTION	SIZE	LAMP(S)
P5607-09	Brushed Nickel	One-light wall lantern	4-1/2" W., 8-5/8" ht. Extends 6-1/8". H/CTR 2-3/4".	1 medium base, 100w max.
P5607-10	Polished Brass			
P5607-20	Antique Bronze			
P5607-31	Black			



P5607-09



P5607-10



P5607-20



P5607-31

FINISHES

- Brushed Nickel - 09
- Polished Brass - 10
- Antique Bronze - 20
- Black - 31

BEVELED GLASS

Octagonal close-to-ceiling fixtures. Clear, bound beveled glass. Damp location listed.

PRODUCT NO.	FINISH	DESCRIPTION	SIZE	LAMP(S)
P5788-09	Brushed Nickel	Three-light	9-3/4" dia., 5-7/8" ht.	3 candelabra base, each 25w max.*
P5788-10	Polished Solid Brass			
P5788-20	Antique Bronze			
P5789-09	Brushed Nickel	Four-light	11-1/8" dia., 6-1/4" ht.	4 candelabra base, each 25w max.*
P5789-10	Polished Solid Brass			
P5789-20	Antique Bronze			

FINISHES

- Brushed Nickel - 09
- Polished Brass - 10
- Antique Bronze - 20



P5788-10



P5789-10



P5788-09



P5789-09



P5788-20



P5789-20

*G16.5 lamp recommended

MOTION LANTERN

Integral motion sensor automatically turns fixture on when guests approach. Adjustable timer and sensitivity settings on back plate.

FINISH

- Black - 31

WALL LANTERN

P5662-31 Black
Clear beveled glass.
5-5/8" W., 12-5/8" ht.
Extends 6-1/2". H/CTR 5-3/4".
One medium base lamp,
100w max.



P5662-31

CAST LANTERN

Cast aluminum with Shatter resistant clear acrylic diffuser.

FINISH

- Black - 31

WALL LANTERN

P5826-31 Black
8" W., 14-1/8" ht.
Extends 10-1/4". H/CTR 10-1/4".
One medium base lamp,
75w max.



P5826-31

UTILITY

Dress up essential lighting with finesse to match any décor, Globe or cylindrical marine glass for clean, minimalist look.

FINISHES

- White - 30
- Black - 31

PRODUCT NO.	FINISH	DESCRIPTION	SIZE	LAMP(S)
P5602-30 P5602-31	White Black	One-light with clear marine glass	4-1/2" W., 7-1/4" ht. Extends 5-1/2". H/CTR 2-1/4".	1 medium base 75w max.
P5603-30 P5603-31	White Black	One-light with clear marine glass	4-7/8" dia., 6-1/4" ht.	1 medium base, 60w max.
P5604-30 P5604-31	White Black	One-light with white 5-3/4" glass globe	5-3/4" W., 8-3/8" ht. Extends 6-1/2". H/CTR 2-1/4".	1 medium base, 100w max.



P5602-31



P5602-30



P5603-31



P5603-30



P5604-31



P5604-30

CEILING MOUNT

Antique Bronze, White or Black finish, textured glass or white acrylic panels.

FINISHES

- White - 30
- Antique Bronze - 20
- Black - 31

METAL

PRODUCT NO.	FINISH	DESCRIPTION	SIZE	LAMP(S)
P5727-20 P5727-31	Antique Bronze Black	One-light ceiling light. Textured glass.	7-1/2" sq., 5" ht.	1 medium base 60w max.
P5729-20 P5729-31	Antique Bronze Black	Two-light ceiling light. Textured glass.	9-1/4" sq., 5" ht.	2 medium base, each 60w max.



P5727-20



P5729-31



P5744-31



P5744-30

POLYCARBONATE

PRODUCT NO.	FINISH	DESCRIPTION	SIZE	LAMP(S)
P5744-30 P5744-31	White Black	Ceiling light with white acrylic panels.	8-1/4"sq., 4-3/4" ht.	1 medium base, 60w max.
P5745-30 P5745-31	White Black	Ceiling light with white acrylic panels.	10-1/4" sq., 5-1/2" ht.	2 medium base, each 60w max.

See page 574 for CFL versions and page 577 for LED versions of this fixture.



P5745-31



P5745-30

NEWPORT NON-METALLIC LANTERNS

Tiered pagoda outdoor light fixtures. Clear prismatic polycarbonate diffusers. UV stabilized to prevent fading. Polypropylene lanterns will not rust.

FINISHES

- White - 30
- Black - 31

PRODUCT NO.	FINISH	DESCRIPTION	SIZE	LAMP(S)
P5444-30 P5444-31	White Black	Post lantern	10" dia., 10" ht. Fits 3" post (order separately).	1 medium base, 60w max.
P5493-31	Black	Post lantern	28-3/4" W., 13" ht. Fits 3" post (order separately).	2 medium base, each 60w max.
P5645-30 P5645-31	White Black	Wall lantern	10" W., 10" ht. Extends 11". H/CTR 5-1/2".	1 medium base, 60w max.



P5493-31



P5645-30



P5645-31



P5444-30



P5444-31

MANSARD

Four-sided gambrel-style hip roof non-metallic outdoor lanterns in classic White or Black finishes.

FINISHES

- White - 30
- Black - 31

PRODUCT NO.	FINISH	DESCRIPTION	SIZE	LAMP(S)
P5414-30 P5414-31	White Black	Post lantern	8" sq., 12" ht. Fits 3" post (order separately).	1 medium base, 60w max.
P5814-30 P5814-31	White Black	Wall lantern	8" W., 12-3/4" ht. Extends 8-1/4". H/CTR 10-5/8".	1 medium base, 60w max.
P5815-30 P5815-31	White Black	Wall lantern with tail	8" W., 17" ht. Extends 8-1/4". H/CTR 10-5/8".	1 medium base, 60w max.



P5414-30



P5814-30



P5814-31



P5815-30



P5414-31

NON-METALLIC LANTERNS

Non-metallic incandescent lanterns available in classic White or Black finishes. Classic outdoor lantern lines. Clear beveled acrylic panels.

FINISHES

- White - 30
- Black - 31

PRODUCT NO.	FINISH	DESCRIPTION	SIZE	LAMP(S)
P5456-30 P5456-31	White Black	Post lantern	8" sq., 18" ht. Fits 3" post (order separately).	1 medium base, 100w max.
P5656-30 P5656-31	White Black	Wall lantern	8" W., 20" ht. Extends 9". H/CTR 15".	1 medium base, 100w max.
P5657-30 P5657-31	White Black	Wall lantern with tail	8" W., 25" ht. Extends 9". H/CTR 15".	1 medium base, 100w max.



P5456-30



P5656-30



P5656-31



P5657-30



P5657-31



P5456-31

PRODUCT NO.	FINISH	DESCRIPTION	SIZE	LAMP(S)
P5737-30 P5737-31	White Black	Wall lantern	8" W., 16" ht. Extends 8-1/2". H/CTR 13".	1 medium base, 60w max.
P5738-30 P5738-31	White Black	Wall lantern with tail	8" W., 21" ht. Extends 8-1/2". H/CTR 13".	1 medium base, 60w max.







P5737-30



P5738-31

LED BULKHEADS

Robust and energy efficient, LED bulkheads are a general-purpose luminaire. Comprised of a die-cast aluminum frame and polycarbonate diffuser. Fixtures are impact resistant and offer various mounting options and can be widely adopted for indoor and outdoor applications.

PRODUCT NO.	FINISH	DESCRIPTION	MOUNTING	SIZE	LAMP(S)
P3647-3030K9 P3647-3130K9	White Black	Oval	Wall or ceiling	6-1/2" W., 10-1/2" ht. Extends 4-3/8". H/CTR 5-1/4".	1 9w LED, module included. 
P3648-3030K9 P3648-3130K9	White Black	Round	Wall or ceiling	9-1/2" dia., 4-3/8" ht. H/CTR 4-3/4".	1 17w LED module included. 
P3649-3030K9 P3649-3130K9	White Black	Oval	Wall or ceiling	6-1/2" W., 10-1/2" ht. Extends 4-1/2". H/CTR 5-1/4".	1 9w LED, module included. 
P3650-3030K9 P3650-3130K9	White Black	Round	Wall or ceiling	9-1/2" dia., 4-1/2" ht. H/CTR 4-3/4".	1 17w LED, module included. 



P3647-3030K9
shown wall-mounted



P3647-3130K9
shown ceiling-mounted



P3648-3130K9
shown wall-mounted



P3648-3030K9
shown ceiling-mounted



P3649-3130K9
shown wall-mounted



P3649-3030K9
shown ceiling-mounted



P3650-3130K9
shown wall-mounted



P3650-3030K9
shown ceiling-mounted

FINISHES

- White - 30
- Black - 31

LED FEATURES

- 120V AC Replaceable LED module
- 17w: 1211 lumens, 71.2 lumens/watt
9w: 623 lumens, 69.2 lumens/watt
- 3000K color temperature; 90+ CRI
- TM-21 60,000 hr. life
- Dimmable to 10% with many ELV type dimmers

PROGRESS **LED**

BULKHEADS

Die-cast aluminum with clear glass lens.

PRODUCT NO.	FINISH	DESCRIPTION	MOUNTING	SIZE	LAMP(S)
P3706-30 P3706-31	White Black	Oval	Wall or ceiling	6-3/8" W., 11" ht. Extends 5". H/CTR 5-1/2".	1 medium base lamp, 100w max.
P3709-30 P3709-31	White Black	Round	Wall or ceiling	7-7/8" dia., 4-1/2" ht. H/CTR 4".	1 medium base lamp, 60w max.



P3709-30
shown wall-mounted



P3709-31
shown ceiling-mounted



P3706-30
shown wall-mounted



P3706-31
shown ceiling-mounted

FINISHES

- White - 30
- Black - 31



POLYCARBONATE BULKHEADS

Virtually maintenance free fixtures. Install on ceilings or walls. Classic white details and trim, Corrosion, impact and shatter resistant, UV stabilized.

FINISHES

○ White - 30

PRODUCT NO.	FINISH	DESCRIPTION	MOUNTING	SIZE	LAMP(S)
P5702-30	White	Round	Wall or ceiling	10" dia., Extends 4-3/4".	1 medium base, 75w max.
P5703-30	White	Round with grill	Wall or ceiling	10-3/8" dia., Extends 5-7/8".	1 medium base, 75w max.
P5704-30	White	Oval	Wall	10-1/2" L., 5-5/8" W. Extends 3-3/4".	1 medium base, ADA 60w max.
P5705-30	White	Oval with grill	Wall	10-1/2" L., 5-7/8" W. Extends 4".	1 medium base, ADA 60w max.
P5706-30	White	Hooded	Wall	10-1/2" L., 5-7/8" W. Extends 4-1/8".	1 medium base, ADA 60w max.

PRODUCT NO.	FINISH	DESCRIPTION	BALLAST	SIZE	LAMP(S)	ADA
P7338-30EBWB	White	Two-light oval wall or ceiling mount.	120V NPF electronic	6" W., 10-5/8" L., Extends 4".	2 13w triple tube CFL. GX24q-1 base. (included)	
P7339-30EBWB	White	Two-light oval wall	120V NPF electronic	6" W., 10-5/8" L., Extends 4".	2 13w triple tube CFL. GX24q-1 base. (included)	



P5702-30



P5703-30



P5704-30



P5705-30
P7338-30EBWB



P5706-30
P7339-30EBWB

WHITE ACRYLIC GLOBES

Shatter-resistant globe ideal for range of outdoor areas.

Cast aluminum wall mounts in White or Black finish.

FINISHES

○ White - 30

● Black - 31

PRODUCT NO.	FINISH	DESCRIPTION	SIZE	LAMP
P5426-60	White	One-light post lantern white fitter	12" dia., 11-7/8" ht. Fits 3" post (order separately).	1 medium base, 100w max.
P5436-60	White	One-light post lantern white fitter	14" dia., 14" ht. Fits 3" post (order separately).	1 medium base, 150w max.
P5478-60	White	One-light post lantern with black polycarbonate fitter. Twist-lock globe.	10" dia., 13-1/8" ht. Fits 3" post (order separately).	1 medium base, 100w max.
P5626-60	Black	One-light cast aluminum wall torch	8" W., 15" ht. Extends 10". H/CTR 8".	1 medium base, 100w max.
P5636-60	Black	One-light cast aluminum wall torch	10" W., 17" ht. Extends 11". H/CTR 10-3/8".	1 medium base, 150w max.



P5626-60

P5636-60



P5436-60

P5426-60

P5478-60

POLYCARBONATE LANTERNS

Durable construction polycarbonate lanterns.

FINISHES

○ White - 30

● Black - 31

PRODUCT NO.	FINISH	DESCRIPTION	SIZE	LAMP
P5612-30 P5612-31	White Black	Polycarbonate wall lantern with clear Lexan diffuser	4-3/4" W., 7-1/4" ht. Extends 5-3/4". H/CTR 2-1/2".	1 medium base, 60w max.
P5813-30 P5813-31	White Black	Polycarbonate wall bracket with 6" acrylic globe	6" W., 7-3/4" ht. Extends 6-1/2". H/CTR 2-1/2".	1 medium base, 60w max.
P5817-31	Black	Polypropylene wall lantern with white acrylic diffuser	4-3/8" W., 7" ht. Extends 5-3/4". H/CTR 3-1/4"	1 medium base, 60w max.
P5818-30 P5818-31	White Black	Polypropylene wall lantern with textured acrylic panels	7-1/4" W., 7-3/4" ht. Extends 5-3/4". H/CTR 2-1/2".	1 medium base, 60w max.
P5844-30 P5844-31	White Black	One-light polypropylene wall bracket with white acrylic diffuser	6" W., 8-3/4" ht. Extends 7-1/4". H/CTR 3".	1 medium base, 60w max.



P5612-30



P5612-31



P5817-31



P5818-30



P5818-31



P5813-31



P5844-30



P5844-31

NON-METALLIC LED

120/277v input voltage. Durable non-corrosive UV resistant housing and diffuser. Thermally protected LED array, 4000k. Wet location listed.


FINISH

● Black - 31

PROGRESS LED



P3715-31

PRODUCT NO.	FINISH	DESCRIPTION	SIZE	LAMP(S)
P3715-31	Black	Wall lantern. 11.3w input power.	6" sq., 9" ht. H/CTR 4-1/4" Extends 7".	4 LED array 10w 




NON-METALLIC

Classic White or Black outdoor lanterns.

FINISHES

○ White - 30

● Black - 31

PRODUCT NO.	FINISH	DESCRIPTION	SIZE	LAMP(S)
P5816-30WB	White	Polycarbonate wall lantern	6" W., 7-3/4" ht. Extends 6-1/2".	1 18w CFL GU24 base (included) 
P5816-31WB	Black			
P5843-30WB	White	Wall lantern	8-1/4" W., 17-5/8" ht. Extends 8-1/2" H/CTR 9-3/4".	1 18w CFL GU24 base (included) 
P5843-31WB	Black			
P5881-30WB	White	Wall lantern w/white acrylic	6" W., 8-7/8" ht. Extends 6-7/8" H/CTR 4-1/8".	1 18w CFL GU24 base (included) 
P5881-31WB	Black			



P5843-30WB



P5843-31WB



P5816-30WB



P5816-31WB



P5881-30WB





P5881-31WB

NON-METALLIC CFL

Energy efficient fixtures for walls or ceilings. Non-metallic components.

FINISH

○ White - 30

PRODUCT NO.	FINISH	DESCRIPTION	SIZE	BALLAST	LAMP(S)
P7118-30	White	Ceiling or wall mount	12" sq., 2-1/4" ht.	120V NPF	2 13w 2-pin twin CFL. GX23 base. ADA 
P7182-30	White	Ceiling or wall mount	9-1/2" sq., 2" ht.	120V NPF	2 7w or 2 9w 2-pin twin CFL. G23 base. ADA 



P7182-30



P7118-30

HARD-NOX®

Threaded opal glass shades screw directly into fitters. Vapor-proof gaskets and porcelain sockets. Wet location listed.

FINISHES

- Satin Aluminum - 16
- Black - 31

PRODUCT NO.	FINISH	DESCRIPTION	SIZE	LAMP(S)
P5510-16	Satin Aluminum	Ceiling fixture	4-3/4" dia., 6-3/4" ht.	1 medium base, 60w max.
P5511-16 P5511-31	Satin Aluminum Black	Wall fixture	4-1/2" W., 6-3/4" ht. Extends 4-3/4". H/CTR 3-1/4".	1 medium base, 100w max.
P5512-16	Satin Aluminum	Wall fixture. Mount horizontally or vertically.	4-1/2" W., 13" ht. Extends 6". H/CTR 6-1/2".	2 medium base, each 100w max.
P5616-16	Satin Aluminum	Ceiling fixture	6" dia., 7-1/2" ht.	1 medium base, 60w max.



P5510-16



P5616-16



P5511-31



P5511-16



P5512-16

HARD-NOX® INCANDESCENT

Variety of geometric shapes ideal for wide range of outdoor areas.
Wet location listed. For indoor or outdoor use.

FINISHES

- Satin Aluminum - 16
- White - 30
- Black - 31

POLYCARBONATE/ACRYLIC DIFFUSER

PRODUCT NO.	FINISH	DIFFUSER	MOUNTING	SIZE	LAMP(S)
P5691-60 P5691-68	White White	White ribbed Clear prismatic	Wall or ceiling	5-3/4" W., 8-1/4" ht. Extends 4-3/8". H/CTR 4-1/8"	1 medium base, 75w max.
P5695-16	Satin Aluminum	White	Wall	4-1/2" W., 6-3/4" ht. Extends 4-3/4". H/CTR 3-1/4"	1 medium base, 60w max.
P5710-31	Black	White	Wall or ceiling	8-3/4" dia., 5-1/4" ht.	1 medium base, 75w max.
P5711-31	Black	White	Wall or ceiling	12" dia., 5-1/4" ht.	2 medium base, each 75w max.
P5791-60 P5791-68	White White	White ribbed Clear prismatic	Wall or ceiling	10-1/2" sq., 4" ht.	2 medium base, ADA each 75w max.



P5691-60



P5691-68



P5695-16



P5710-31



P5711-31



P5791-60











P5791-68

HARD-NOX®

Variety of geometric shapes ideal for energy efficient illumination.
 Impact resistant durability with polycarbonate or acrylic diffusers.
 Classic White or Black finishes.

FINISHES

- White - 30
- Black - 31

PRODUCT NO.	FINISH	DIFFUSER	DIMENSIONS	UL LISTING	BALLAST	LAMP(S)	
P5694-60	White	White ribbed polycarbonate	5-3/4" W., 8-1/4" ht. Extends 4-3/8". H/CTR 4-1/8".	Wet	120V HPF magnetic	1 2-pin twin 9w CFL. G23 base.	
P7124-60 P7124-68	White	White ribbed DR acrylic Clear prismatic DR acrylic	4-1/4" W., 12-1/4" ht. Extends 4-1/4". H/CTR 6-1/8".	Damp	120V HPF magnetic	1 2-pin twin 13w CFL. GX23 base.	
P7372-30	White	White DR acrylic	13-3/4" dia., 3-1/4" ht.	Damp	120V NPF Rapid start	1 22w FC8T9 and 1 32w FC12T9 circline ADA HPF	
P7372-30STRWB	White	White DR acrylic	13-3/4" dia., 3-1/4" ht.	Damp	120V NPF electronic	2 13w 4-pin Quad CFL. G24q-1 base. (incl) ADA	
P7373-30	White	White DR acrylic	19" dia., 4-1/4" ht.	Damp	120V HPF Rapid start	1 40w FC16T9 and 1 32w FC12T9 circline	
P7375-30STRWB	White	White DR acrylic	9" dia., 3-1/4" ht.	Damp	120V NPF electronic	1 13w 4-pin Quad CFL. G24q-1 base. (incl) ADA	
P7376-30 P7376-31	White Black	White DR acrylic	11" dia. 3-1/4" ht.	Damp	120V NPF magnetic	2 2-pin twin 13w CFL. GX23 base. ADA	
P7376-3030K9	White	Acrylic	11" dia., 3-1/4" ht.	Damp	N/A	1 17w LED module included. 1,711 lumens, 90 CRI	




SHELTON

White acrylic diffuser. Mounts vertically or horizontally.
 Die-cast aluminum construction. Indoor or outdoor.

FINISH

- Brushed Nickel - 09

PRODUCT NO.	FINISH	MOUNTING	SIZE	LAMP(S)	
P5790-09	Brushed Nickel	Wall or ceiling	11" W., 5-5/8 ht." Extends 3-3/4".	1 13w 4-pin twin CFL. G24q-1 base.	ADA 



P5790-09



P5790-09

ALUMINUM LED CYLINDERS

Sleek, cylindrical forms in elegant finish selections. Die-cast aluminum wall brackets and heavy-duty aluminum framing. Fade and chip-resistant. UL listed for wet locations when used with lens cover.

FINISHES

- Bronze - 20
- White - 30
- Black - 31
- Metallic Gray - 82

LED CYLINDER FEATURES

- 120v AC
- 1000 lumens (17w)
- 2000 lumens (29w)
- 3000K color temperature
- Dimmable to 10% brightness with ELV type dimmers

5" ALUMINUM CYLINDERS

PROGRESS **LED**

PRODUCT NO.	FINISH	DESCRIPTION	SIZE	LAMP(S)
P5674-20/30K	Bronze	One-light down*	5" W., 7-1/4" ht. Extends 8". H/CTR 2-1/2".	1 17w LED module included
P5674-30/30K	White			
P5674-31/30K	Black			
P5674-82/30K	Metallic Gray			
P5675-20/30K	Bronze	Two-light up/down For wet locations specify P8799 top cover lens.	5" W., 14" ht. Extends 8". H/CTR 7".	2 17w LED modules included
P5675-30/30K	White			
P5675-31/30K	Black			
P5675-82/30K	Metallic Gray			
P5774-20/30K	Bronze	One-light. Mounts flush to ceiling*	5" dia., 6-1/2" ht.	1 17w LED module included
P5774-30/30K	White			
P5774-31/30K	Black			
P5774-82/30K	Metallic Gray			

*Dark sky.



P5774-20/30K



P5774-30/30K



P5774-31/30K



P5774-82/30K



P5674-20/30K



P5674-30/30K



P5674-31/30K



P5674-82/30K



P5675-20/30K



P5675-30/30K



P5675-31/30K



P5675-82/30K

6" ALUMINUM CYLINDERS

PRODUCT NO.	FINISH	DESCRIPTION	SIZE	LAMP(S)
P5641-20/30K	Bronze	One-light down*	6" W., 12" ht. Extends 8-7/8". H/CTR 4-1/2".	1 29w LED module included
P5641-30/30K	White			
P5641-31/30K	Black			
P5641-82/30K	Metallic Gray			
P5642-20/30K	Bronze	Two-light up/down. For wet location specify P8798 top cover lens.	6" W., 18" ht. Extends 8-7/8". H/CTR 8".	2 29w LED modules included
P5642-30/30K	White			
P5642-31/30K	Black			
P5642-82/30K	Metallic Gray			
P5741-20/30K	Bronze	One-light cylinder. Mounts flush to ceiling or hangs with pendant accessory kit, page 301.	6" dia., 12" ht.	1 29w LED module included
P5741-30/30K	White			
P5741-31/30K	Black			
P5741-82/30K	Metallic Gray			

*Dark sky.



P5741-20/30K



P5741-30/30K



P5741-31/30K



P5741-82/30K



P5641-20/30K



P5641-30/30K



P5641-31/30K



P5641-82/30K



P5642-20/30K



P5642-30/30K



P5642-31/30K



P5642-82/30K



Shown: P5642-30

ALUMINUM CYLINDERS

Sleek, cylindrical forms in elegant finish selections. Die-cast aluminum wall brackets and heavy-duty aluminum framing. Fade and chip-resistant. UL listed for wet locations when used with lens cover.

FINISHES

- Bronze - 20
- White - 30
- Black - 31
- Metallic Gray - 82

5" ALUMINUM CYLINDERS

PRODUCT NO.	FINISH	DESCRIPTION	SIZE	LAMP(S)
P5674-20	Bronze	One-light down	5" W., 7-1/4" ht. Extends 8". H/CTR 2-1/2".	1 75w PAR-30 or 75w BR-30
P5674-30	White			
P5674-31	Black			
P5674-82	Metallic Gray			
P5675-20	Bronze	Two-light up/down For wet locations specify P8799 top cover lens.	5" W., 14" ht. Extends 8". H/CTR 7".	2 75w PAR-30
P5675-30	White			
P5675-31	Black			
P5675-82	Metallic Gray			
P5774-20	Bronze	One-light. Mounts flush to ceiling	5" dia., 6-3/4" ht.	1 75w PAR-30 or 75w BR-30
P5774-30	White			
P5774-31	Black			



P5675-20



P5675-82



P5774-20



P5774-30



P5774-31



P5674-31



P5674-20



P5674-82

6" ALUMINUM CYLINDERS

PRODUCT NO.	FINISH	DESCRIPTION	SIZE	LAMP(S)
P5641-20	Bronze	One-light down	6" W., 12" ht. Extends 8-7/8". H/CTR 4-1/2".	1 250w PAR-38 or 150w BR-40
P5641-30	White			
P5641-31	Black			
P5641-82	Metallic Gray			
P5642-20	Bronze	Two-light up/down. For wet location specify P8798 top cover lens.	6" W., 18" ht. Extends 8-7/8". H/CTR 8".	2 250w PAR-38 or 150w BR-40
P5642-30	White			
P5642-31	Black			
P5642-82	Metallic Gray			
P5741-20	Bronze	One-light cylinder. Mounts flush to ceiling or hangs with pendant accessory kit, page 624.	6" dia., 12" ht.	1 250w PAR-38 or 150w BR-40
P5741-30	White			
P5741-31	Black			



P5741-30



P5741-31



P5641-31



P5641-82



P5642-20

ALUMINUM SQUARES


Heavy-duty aluminum construction, die-cast aluminum wall bracket. UL listed for wet locations. Powder coat for chipping and fading resistance. Dark Sky compliant for down light only.

FINISHES

- Bronze - 20
- White - 30
- Black - 31

PRODUCT NO.	FINISH	DESCRIPTION	SIZE	LAMP(S)
P5643-20	Bronze	One-light 6" square	6" W., 12" ht. Extends 8-7/8". H/CTR 4-1/2".	1 250w PAR-38 or 150w BR-40
P5643-30	White			
P5643-31	Black			
P5644-20	Bronze	Two-light 6" up/down square*	6" W., 18" ht. Extends 8-7/8". H/CTR 8".	2 250w PAR-38 or 150w BR-40
P5644-30	White			
P5644-31	Black			

*For use in wet locations, specify P8797-31 top cover.



ALUMINUM LED SQUARES

Heavy-duty aluminum construction, die-cast aluminum wall bracket. UL listed for wet locations. Powder coat for chipping and fading resistance. Dark Sky compliant for down light only. 3000K, 90+ CRI.

FINISHES

- Bronze - 20
- White - 30
- Black - 31
- Metallic Gray - 82

PRODUCT NO.	FINISH	DESCRIPTION	SIZE	LAMP(S)
P5643-2030K	Bronze	One-light 6" square LED	6" W., 12" ht. Extends 8-7/8". H/CTR 4-1/2".	1 29w LED module included
P5643-3030K	White			
P5643-3130K	Black			
P5643-8230K	Metallic Gray			
P5644-2030K	Bronze	Two-light 6" LED up/down square*	6" W., 18" ht. Extends 8-7/8". H/CTR 8".	2 29w LED modules included
P5644-3030K	White			
P5644-3130K	Black			
P5644-8230K	Metallic Gray			

*For use in wet locations, specify P8797-31 top cover.



POLYMERIC CYLINDERS

Sleek, cylindrical forms ideal for coastal locations. Up or down configuration. Non-corrosive components withstand salt, wind, sand, water and sun. Down version shields par lamp and bug lights to minimize glare onto beach for turtle law compliance. Wet location listed. Dark Sky compliant Down Light Only.

FINISHES

○ White - 30

● Black - 31

PRODUCT NO.	FINISH	DESCRIPTION	SIZE	LAMP(S)
P5712-30	Textured White	One-light polymeric cylinder	5" W., 7-1/4" ht. Extends 7-3/4".	1 75w PAR-30 or 65w BR-30
P5712-31	Black			
P5713-30	Textured White	Two-light polymeric cylinder*	5" W., 14" ht. Extends 7-3/4".	2 75w PAR-30 or 65w BR-30
P5713-31	Black			
P8712-30	Textured White	Turtle-friendly accessory	5" dia., 4" ht.	n/a
P8712-31	Black			

*Wet location listed with P8799 top cover.



P8712-30



P8712-31



P5712-30



P5712-31



P5713-30



P5713-31

ACCESSORIES FOR SQUARES & CYLINDERS

DEEP GROOVE STEP BAFFLES

Black anodized aluminum to minimize glare

PRODUCT NO.	FINISH	DESCRIPTION	SIZE
P8710-31	Black	Deep groove step baffle for P5641, P5642 and P5741 6" cylinders.	6" dia., 4" ht.



P8710-31

PENDANT KIT

Pendant kit adapts P5741 ceiling fixture to 6", 12" or 18" stem mounting. Includes canopy, hang-straight swivel, 6" and 12" sections with coupling.

PRODUCT NO.	FINISH	DESCRIPTION
P8741-20	Bronze	Pendant kit for P5741
P8741-30	White	
P8741-31	Black	

TOP COVER LENS

Adapts up/down fixtures for wet location use. Heat & shatter-resistant clear tempered lens w/black trim.


PRODUCT NO.	FINISH	DESCRIPTION	SIZE
P8797-31	Black	Top cover lens for P5644 6" squares	6" sq.
P8798-31	Black	Top cover lens for P5642 6" cylinders	6" dia.
P8799-30	White	Top cover lenses for P5675 & P5713 5" cylinders	5" dia.
P8799-31	Black		



P8797-31



P8798-31
P8799-31



P8741-30

NON-METALLIC PAR LAMPHOLDERS

Ideal for environmental conditions where metallic fixtures are undesirable. UV stabilized non-metallic materials and non-corrosive hardware.

FINISHES

- Bronze - 20
- White - 30
- Black - 31

P5202-20 Bronze

P5202-31 Black

Single painted adjustable swivel floodlight. Aluminum construction. Locking adjustment. 5-7/8" dia., 9" ht. One PAR38, 150w max.



P5202-20



P5202-31

P5203-20 Bronze

P5203-30 White

P5203-31 Black

Two painted adjustable swivel floodlights with lamp shroud. Aluminum construction. 6-1/4" dia., 9" ht. Two PAR38, each 150w max.



P5203-20



P5203-31

P5207-30 White

Two painted adjustable swivel floodlights. Aluminum construction. Locking adjustment. 4-7/8" dia., 6-3/4" ht. Two PAR20, PAR30 or PAR38, each 150w max.



P5207-30

P5212-20 Bronze

P5212-30 White

Double non-metallic PAR lampholder. 11" W., 4-5/8" ht. Extends 5". One PAR 38, 120w max.




P5212-20



P5212-30

P5214-30 White

PAR lampholder shroud for P5212. 6-5/8" dia., 5-1/8" ht.



P5214-30

SECURITY LIGHTING

These LED swivel flood lights have tempered glass and rugged die cast construction. Can be used as single or multiple heads. Order backplate, motion sensor and floodlight separately or a complete fixture.

FINISHES

- Antique Bronze - 20
- White - 28
- Metallic Gray -82

FLOOD LIGHT WITH MOTION SENSOR

P6341-2030K Antique Bronze

P6341-2830K White

P6341-8230K Metallic Gray

Two flood lights with backplate and motion sensor.

6-3/4" W., 6" ht.

Two 13w LED included.



FLOOD LIGHT HEAD

P6342-2030K Antique Bronze

P6342-2830K White

P6342-8230K Metallic Gray

3-3/4" dia., 5" ht.

Extends 3-1/4".

13w LED included.



BACK PLATE

P6343-20 Antique Bronze

P6343-28 White

P6343-82 Metallic Gray

Five KO gaskets included.

Die cast aluminum construction.

4-3/4" dia.

180° MOTION SENSOR

P6345-20 Antique Bronze

P6345-28 White

P6345-82 Metallic Gray

180° motion sensor for use with P6343 flood lights and P6343 backplate.

5-1/2" W., 1-7/8" ht.

FLOOD LIGHT WITH SPIKE

P6346-2030K Antique Bronze

P6346-2830K White

P6346-8230K Metallic Gray

Flood light with spike for ground installation.

3-3/4" dia., 13" ht.

13w LED included.

LED FEATURES

- 1000 lumens
- 3000K color temperature
- 60,000 hr. life
- Wet location listed
- Multi-directional swivel joint



P6341-2030K



P6343-20



P6341-2830K



P6343-20

shown with two P6342-2030K heads



P6341-8230K



P6346-2030K



P6342-2030K



P6345-20



P6346-2830K



P6342-2830K



P6345-28



P6342-8230K



P6345-82



P6346-8230K



ADDRESS LIGHTS

Long lamp life (50,000 hours) and weather resistant. Housing constructed from high-grade polypropylene. Stainless steel mounting hardware and lamps included. Complies with municipal codes that require illuminated house numbers. Order 16V transformer separately.

ADDRESS LIGHT HOUSING

Numbers, letters and blanks must be ordered separately from address light fixture. * Not UL Listed

PRODUCT NO.	FINISH	DESCRIPTION	SIZE	LAMP(S)
P5968-31WB*	Black	Two-light address light housing 12V	12-1/2" W., 6-3/4" ht. Extends 2-1/4".	2 T-3/1/4 5w xenon wedge base lamps included.
P5969-01	n/a	Transformer 16V 10w for P5968	2" W., 1-3/4" L.	n/a



P5968-31WB



P5969-01

ADDRESS NUMBERS

Numbers, letters and blanks must be ordered separately from address light fixture, P5968. Ten numbers per pack. Not UL Listed.

PRODUCT NO.	DESCRIPTION	SIZE
P5970-000	0	2-1/4" W., 5" ht.
P5970-001	1	
P5970-002	2	
P5970-003	3	
P5970-004	4	
P5970-005	5	
P5970-006	6 or 9	
P5970-007	7	
P5970-008	8	
P5970-HLF	1/2	
P5970-FBK	Full Blank	
P5970-HBK	Half Blank	1-1/8" W., 5" ht.



P5970-000

P5970-001

P5970-002

P5970-003

P5970-004

P5970-005

P5970-006*

P5970-007

P5970-008

P5970-FBK

P5970-HBK

P5970-HLF

DOOR CHIME

Includes transformer, chime assembly and lighted push button.

PRODUCT NO.	FINISH	DESCRIPTION	SIZE
PC001-30	Textured White	One-chime kit with 10va transformer	4" W., 7-3/16" ht Depth 2".



PC001-30

PHOTO CONTROL

Remote mount photo control installs into standard, rain-tight junction box and includes faceplate and gasket. Max load 2000 watts. Operating range -40 + 140F. Consumes less than 1 watt.

PHOTOCONTROL

PTORK3010 Unfinished
3" W., 5" ht.



PTORK3010

PEDESTAL MOUNT FOR LANTERNS

Aluminum construction offers virtually maintenance-free benefits and sturdy operation that will last over time. Works with 3" filter lanterns. Cannot mount to poles.

FINISHES

- Antique Bronze - 20
- Black - 31

PRODUCT NO.	FINISH	DESCRIPTION	SIZE
P8726-20	Antique Bronze	Cast aluminum pedestal mount. For mounting post lanterns with 3" fitters on pedestals or on top of walls.	7" dia., 3-1/4" ht.
P8726-31	Black		



P8726-20



P8726-31

NIGHT-SAVER® SHIELD

Shield fits over A-19 medium base bulb to provide Dark Sky friendly illumination.

FINISHES

- Antique Bronze - 20
- Black - 31

PRODUCT NO.	FINISH	DESCRIPTION	SIZE
P8709-20	Antique Bronze	Nightsaver® lamp shade.	3" bottom., 2-1/2"W. top.
P8709-31	Black		
P8400-31	Black	Small dark sky shield	4" dia., 5-7/8" ht.
P8401-31	Black	Medium dark sky shield	5-1/4" dia., 8-1/8" ht.
P8402-31	Black	Large dark sky shield	6-1/2" dia., 10-1/8" ht.



P8709-20



P8709-31

DARK SKY COMPATIBILITY LIST FOR 8400/8401/8402

FAMILY NAME	SMALL	MEDIUM	LARGE
ESSENTIAL (page 683)			
P6059	P8400		
P6060		P8401	
P6086			P8402
P6512		P8401	
RESORT (page 641)			
P5987	P8400		
P5988		P8401	
P5989			P8402
P6504		P8401	
P6606			P8402
PRARIE (page 682)			
P5763	N/A		
P5764		P8401	
P5563		P8401	
P5463		P8401	



P8400-31



P8401-31



P8402-31

POSTS

Surround your home with decorative posts to add style and elegance for years to come. Aluminum construction and popular finish choices add to functionality of outdoor lighting.

FINISHES

- Antique Bronze - 20
- White - 30
- Black - 31

PRODUCT NO.	FINISH	DESCRIPTION	SIZE
P5390-20 P5390-31	Antique Bronze Black	Aluminum post.	3" dia., 7' ht. (Can be cut to desired length)
P5390-31PC	Black	Aluminum post with photocell which automatically turns on at dusk, off at dawn.	3" dia., 7' ht. (Can be cut to desired length)
P5391-30 P5391-31	White Black	Aluminum post with ladder rest.	3" dia., 7' ht. (Can be cut to desired length)
P5391-20PC P5391-31PC	Antique Bronze Black	Aluminum post with ladder rest and photocell which automatically turns lantern on at dusk and off at dawn.	3" dia., 7' ht. (Can be cut to desired length)
P5392-31PC	Black	Black aluminum post with ladder rest, photocell which automatically turns on at dusk off at dawn and weather proof GCO.	3" dia., 7' ht. (Can be cut to desired length)
P5394-31	Black	Commercial grade black aluminum post, .125 wall thickness.	3" dia., 12' ht. (Can be cut to desired length)
P8748-31	Black	Surface Mount Post Adapter Flanged cast aluminum base for surface mounting round 3" bottom O.D. posts. Anchor bolts and allen set screws included.	8" dia., 5" ht.



P5390-20

P5390-31
P5394-31

P5391-20PC



P5391-30



P5391-31PC



P8748-31



Shown: P5988-122 wall lantern and P6404-122 post lantern with P5390-31 post



LANDSCAPE LIGHTING DESIGN TECHNIQUES

Progress Lighting offers the following tips and design techniques to follow when planning landscape design, ensuring your yard will be a wonderful environment where your friends and family can relax.



Path Lighting

Lighting along paths and driveways enhances the overall theme of your outdoor space while preventing accidents in the dark.

- Position lights on alternate sides for even illumination
- Define edges by positioning lights about one foot from one or both sides of the path
- Position lights to avoid shadows when used at steps, as well as away from plants so they don't interfere with light distribution



Uplighting

Highlight or accent distinct plants, trees or accessories in your yard by positioning in-ground lights close to your focal point.

The best way to enhance the texture of objects outdoors is by mounting spotlight or floodlight fixtures on the ground.



Security Lighting

Decorative outdoor lighting designs can also add security features for your home. The majority of residential crimes take place after dark – when thieves feel they cannot be seen.

A well-lit yard can be an excellent crime prevention method and fixture options designed specifically for security, like motion sensors, can add extra protection and convenience. Consider using PAR lampholders on the corners aimed down each wall of your home.



Accent Lighting

Also known as spot lighting, this effect uses cross lighting and uplighting techniques to showcase a particular item in your garden with bright light in an otherwise dark area. Use an accessory shield to avoid glare.



Decks and Porches

It's important to outline the perimeters of the deck and railings, as well as provide safety for nighttime use on decks and outdoor porches. Use low voltage (12V) fixtures for maximum electrical safety.



Grazing

Grazing light is an effect that illuminates the outline of a particular tree, shrub or architectural feature to enhance its shape and texture. This must be done precisely and it usually requires mounting a carefully positioned spotlight 6 to 12 inches from the surface.



Shadowing

Add an elegant, but mysterious, touch to your outdoor design with this effect. Shadow lighting is typically achieved with uplighting placed out of sight to create silhouette images of trees, plants, and accessories.



Silhouetting

Produce an awe-inspiring effect by placing light fixtures directly behind your subject. Lights mounted near the bottom of a tree or shrub will cast the plant's shadow against the sky for an intriguing twilight display. This technique is often used near the home for an appealing façade.



Step Lighting

To increase safety, step lighting uses small fixtures that are typically shielded to cast a soft, glare-free light across steps and decks.

Install one step light on every other riser and use louvered wall plates to avoid glare.

LED PATH

Several LED landscape lighting options are available for popular exterior applications. Low voltage LED landscape, bollard and path lights enhance outdoor settings, while adding safety, security and curb appeal to areas around the home. 3000K color temperature.



P5245-20



P5245-31



P5298-31



P5246-31

PATH LIGHT

P5245-20 Antique Bronze*

P5245-31 Black*

Die cast aluminum construction. Includes stake and deck mount, 6-1/2" dia., 20-3/4" ht. Extends 9-1/2".

One 1.5w LED module included.

PATH LIGHT

P5298-31 Black*

Die cast aluminum construction. Includes stake and deck mount, 4' cable and connector. 6" dia., 17-1/2" ht. One 1.5w LED module included.

LINEAR PATH LIGHT

P5246-31 Black*

Linear path light with ground stake. Die cast aluminum construction with louvered glass. 5-3/8" W., 2-3/8" ht. Extends 4-3/8". One 1.5w LED module included.



P5247-09



P5247-31



P5297-31



P8270-31

BOLLARD

P5247-09 Brushed Nickel*

P5247-31 Black*

Slim bollard with cast aluminum construction. Frosted internal diffuser surrounded by clear plastic. 2-5/8" dia., 24" ht.

One 1.5w LED module included.

SPREAD LIGHT

P5297-31 Black*

Die cast aluminum construction. Includes stake and deck mount, 4' cable and connector. 7" dia., 16-1/2" ht.

One 1.5w LED module included.

LED TRANSFORMER

P8270-31 Non metallic case protects timer controls and 120v to 12v transformer. Surge protected with grounded cord/plug set and easy 12V cable attachment. Photocontrol triggers "time on", eliminating seasonal adjustment. 56w max. Non-dimmable. Recommend using 14 gauge cable P8617 or P8626, page 749. 4-1/8" W., 5-5/8" ht., 3-1/2" depth.

*All LED Landscape lighting must be used with transformer P8270-31. Recommend using 14 gauge cable (P8716 or P8626) page 749.

PROGRESS LED



Shown: P5298-31 Path Light



Shown: P5275-31 path lights

PATH LIGHTS

Lighting walkways, paths, steps and driveways will welcome your guests and help prevent unwanted accidents. The first impression of a home or business is the entryway, and it is important that care be taken to light it properly.



P5250-20



P5250-31



P5253-20



P5257-20

ASHMORE

P5250-20 Antique Bronze


P5250-31 Black

Water seeded glass. Cast aluminum construction.

6-1/2" W., 25" ht.

Extends 9-1/2".

One 12V T5 wedge base,

18w max. included. 

CAST ALUMINUM SHADE


P5253-20 Antique Bronze

With wire guard and etched glass enclosure. Solid brass stem.

6" W., 26" ht.

Extends 6-7/8".

One 12V T5 wedge base,

18w max. included. 

COPPER


P5257-20 Antique Bronze

Path light with clear optic seeded glass. Solid brass construction.

7-1/2" dia., 26" ht.

Extends 9-7/8".


One 12V T5 wedge base,

18w max. included. 



P5258-31WB


ARRIVE

P5258-31WB Black
Textured water glass.
5" W., 27" ht.
One 12V T5 wedge base,
18w max. included. 



P5261-46


MISSION

P5261-46 Weathered Bronze
Light honey art glass.
Solid brass construction.
6-1/2" sq., 19-3/8" ht.
Extends 5-1/4".
One 12V T5 wedge base,
18w max. included. 



P5271-20


TIFFANY ART GLASS

P5271-20 Antique Bronze
Green art glass shade
suspended from detailed arm.
Solid brass construction.
6-7/8" dia., 23" ht.
Extends 9-1/4".
One 12V T5 wedge base,
18w max. included. 



P5272-46

ARTS & CRAFTS

P5272-46 Weathered Bronze
Light honey art glass panels.
Solid brass construction.
5-1/2" W., 28-3/4" ht.
Extends 6-5/8".
One 12V T5 wedge base,
18w max. included. 



P5273-46


MISSION

P5273-46 Weathered Bronze
Light honey art glass.
Solid brass construction.
Square stem included with
1/2 NPS thread.
6-1/2" sq., 30" ht.
One medium base lamp,
60w max. (line voltage)



P5275-31


COVENTRY


P5275-31 Black
Water seeded glass.
5-3/4" dia., 25" ht.
Extends 5-3/4".
One 12V T5 wedge base,
18w max. included. 



P5276-71

CRANBROOK

P5276-71 Gilded Iron
Tiffany art glass
5-1/8" dia., 25" ht.
Extends 6-1/4".
One 12V T5 wedge base,
18w max. included. 


All low voltage  fixtures include:
1/2 NPS threaded adapter connector
(P8651) mounting stake (P8618-31),
and lamp. Must be connected to a
12V transformer, page 748.

SPREAD LIGHTS



P5238-31WB

SPREAD LIGHT

P5238-31WB Black
Cast aluminum construction.
Twist off cover for easy relamping.
6-1/2" dia., 13" ht.
One 12V halogen bi-pin,
20w max. included. 



P5265-31

DOMES


P5265-31 Black
Cast aluminum construction.
White innerlined shade for
maximum light output.
9" dia., 26-3/4" ht.
One medium base A-19 lamp,
100w max.

LINEAR



P5246-31

LINEAR PATH LIGHT


P5246-31 Black
Linear path light with ground
stake. Die cast aluminum
construction with louvered glass.
Use with P8270-31 transformer.
5-3/8" W., 2-3/8" ht.
Extends 4-3/8".
One 1.5w LED module included. 

PROGRESS  LED



P5200-20

LINEAR PATH LIGHT

P5200-20 Antique Bronze
Cast solid bronze.
Furnished with stake.
7" W., 1-7/8" ht.
One 12-volt T5 wedge base,
18w max. included. 

PAGODA



P5204-38



P5204-31





P5219-31

PAGODA

P5204-38 Green
P5204-31 Black
Die-cast aluminum. Clear glass liner.
1/2 NPS threaded fitting for
permanent or P5233 for
portable installation.
Cannot be used with P5312-31.
6" dia., 7-1/8" ht.
One medium base lamp,
100w max.

PAGODA

P5219-31 Black
Die-cast aluminum. Clear glass liner.
1/2 NPS threaded fitting for
P8667 or P8618 installation.
Cannot be used with P5312-31.
6" dia., 7-1/8" ht.
One 12V T5 wedge base,
18w max included. 

All low voltage  fixtures include:
1/2 NPS threaded adapter connector
(P8651) mounting stake (P8618-31),
and lamp except LED fixtures.
Must be connected to a 12V
transformer, page 748.

BOLLARD

Optional pole mount or mount directly on ground



BOLLARD

P5205-31 Black
Etched glass.
1/2 NPS threaded fitting for permanent or P5233 installation. For Bollard mount order with P5313-31 pole or P8562-31 page 743.
5" dia., 6-1/4" ht.
One medium base lamp, 60w max.

PAGODA

Optional pole mount or mount directly on ground



LARGE PAGODA


P5210-31 Black
Cast aluminum path and driveway light. Clear glass liner. 1/2 NPS threaded fitting for permanent or P5233 installation. For Bollard mount order with P5312-31 pole or P8562-31 page 743.
10" dia., 9-1/2" ht.
One medium base lamp, 100w max.

BOLLARD POLE MOUNT OPTIONS

Mount P5205-31 on top of bollard to spread wider circles of light and to coordinate ground lights with bollards. Aluminum construction with pedestal and "J" bolts for surface mounting on paved areas or atop walls. For complete unit order bollard accessory and light.



P5233-31 Black
7" Cast aluminum spike for portable installation. 15' SJT #18 cord with plug. Accommodates 1/2 NPS threaded fitting. Overall ht. 8-5/8".




P5313-31 Black
Bollard Pole for P5205-31. (order each separately). 4-3/4" dia., 28-3/8" ht. Accepts P5205-31 only.

PAGODA POLE MOUNT OPTIONS

Mount P5210-31 on top of bollard to spread wider circles of light and to coordinate ground lights with bollards. Aluminum construction with pedestal and "J" bolts for surface mounting on paved areas or atop walls. For complete unit order bollard accessory and light.



P5233-31 Black
7" Cast aluminum spike for portable installation. 15' SJT #18 cord with plug. Accommodates 1/2 NPS threaded fitting. Overall ht. 8-5/8".



P5312-31 Black
Bollard Pole for P5210-31. (order each separately). 3-7/8" dia., 28-3/8" ht.



WELL LIGHTS




P5295-31

P5295-31 Black
Die cast aluminum, glass cover. Includes 4' cable and connector. Cannot mount in concrete. 5" dia., 4" ht. One 3w LED module included. Use with P8270-31 transformer.

PROGRESS **LED**




P5228-31



P5228-31 Black
Cast aluminum adjustable well light. Clear glass lens. Twist off cover for easy relamping. Internal gimbal ring adjusts 45° max. 3-1/2" dia., 8-1/2" ht. One 12-volt MR-16, 50w max. 



P5229-31
shown with optional P8613-31
and optional P8684-68

P5229-31 Black
Adjustable well light. Well sleeve is 1/4" thick PVC pipe and installs flush or reversed provides lamp shielding. Inconspicuous "up light" which adjusts to 45° from its concealed in-ground installation. (Requires external transformer.) 6-5/8" dia., 13-1/4" ht. One 12-volt PAR-36, 50w max. 

Note: Glass cover and cube cell louver need to be ordered separately




P8613-31 Black
45° cube cell louver fits under supplied glass lens for glare control. 4-3/4" cube cell for P5229-31, P5235-31 & P5237-31.

P8684-68 Clear
Tempered glass cover for added lamp protection for P5229-31.



P5228-31

All low voltage  fixtures include: 1/2 NPS threaded adapter connector (P8651) mounting stake (P8618-31), and lamp. Must be connected to a 12V transformer, page 748.

FLOOD LIGHTS LINE VOLTAGE



P5234-31

P5234-31 Black

Black powder-coat painted aluminum resists chipping and fading. Clear lens. Locking vertical adjustment. 4-1/2" dia., 6-5/8" long. One PAR 20, 50w max.



P5235-31

P5235-31 Black*

Black powder-coat painted aluminum resists chipping and fading. Clear lens. Locking vertical adjustment. 5-1/4" dia., 8-1/4" long. One PAR 38, 150w max.



P5241-31

P5241-31 Black

Black powder-coat painted cast aluminum resists chipping and fading. Clear lens. Locking vertical adjustment. 4-3/4" dia., 6-5/8" long. One PAR 30, 75w max.

FLOOD LIGHTS LOW VOLTAGE



P5299-31

P5299-31 Black


Adjustable knuckle for aiming. Die cast aluminum. Stake and deck mount, 4' cable and connector included. 4-1/2" dia., 6-5/8" ht. One 3w LED module included. Use with P8270-31 transformer.

PROGRESS **LED**



P5230-31


P5230-31 Black

Miniature low voltage spot light. Black powder coat painted aluminum. Locking vertical adjustment. Mounting stake included. 3" dia., 5" long. One 12V MR16, 50w max. 



P5237-31


P5237-31 Black*

Black powder-coat painted aluminum resists chipping and fading. Locking vertical adjustment. 5-1/4" dia., 5-3/4" length. One 12V PAR-36, 50w max. 



P5239-31WB


P5239-31WB Black

Adjustable hinge door for easy relamping. Includes stake. 5-1/2" W., 6-1/8" ht., 3-1/2" depth. One 12V halogen bi-pin lamp. 50w max included. 



P5279-25

P5279-25 Verde

P5279-31 Black
12V composite accent light. Non-metallic construction and stainless hardware prevent corrosion. 4-1/4" dia., 8-3/4" ht. One MR16, GU5.3 base, 50w max. 



P5279-31

* See page 749 for flood light accent accessories.

SPECIALTY, DECK AND RAIL LIGHTS




P5224-31WB

P5224-31WB Black

Durable cast aluminum is powder-coat painted for superior resistance to chipping, fading and the effects of salt air.

3" W., 1-3/4" ht., extends 1-3/8"

One T5 wedge base,
13w max. included. 



P5223-31WB




P5223-54WB

P5223-31WB Black

P5223-54WB Natural

Durable cast aluminum finishes powder-coat painted to resist chipping, fading and the effects of salt air.

3-1/8" W., 2" ht., extends 1-3/8"

One T5 wedge base,
13w max. included #912. 



P5296-31

P5296-31 Black

Die cast aluminum with black powder-coat finish. Polycarbonate diffuser. 12v AC input. Use with LED transformer P8270-31. 4-1/8" dia., extends 2-1/4"

Three 1.5w LED modules included.

PROGRESS 



P5262-46


MISSION

P5262-46 Weathered Bronze

Rail mount or post lantern.

Fits 4" x 4" post or flush mount.

6-1/2" W., 7-1/2" ht.

One T5 wedge base,
18w max. included. 

LED STEP LIGHTS

5w 3000K color temperature with 84+ CRI and a 120° beam spread. LED step/wall lights are available in a vertical or horizontal configuration for mounting into a single-gang wallbox.

PROGRESS **LED**



P6827-0930K



P6827-3030K

P6827-0930K Brushed Nickel
P6827-2030K Antique Bronze
P6827-3030K White
P6827-3130K Black
 Louvered horizontal step/wall light.
 Wet location listed.
 5-1/4" W. , 3-1/2" ht.
 5w LED module included.



P6828-0930K



P6828-2030K



P6828-3030K



P6828-3130K

P6828-0930K Brushed Nickel
P6828-2030K Antique Bronze
P6828-3030K White
P6828-3130K Black
 Louvered vertical step/wall light.
 Wet location listed.
 3-1/2" W. , 5-1/4" ht.
 5w LED module included.



P6832-0930K



P6832-3130K



P6829-2030K



P6829-0930K

P6829-0930K Brushed Nickel
P6829-2030K Antique Bronze
P6829-3030K White
P6829-3130K Black
 Vertical step/wall light.
 Wet location listed.
 2-3/4" W., 4-1/2" ht.
 5w LED module included.


P6832-0930K Brushed Nickel
P6832-2030K Antique Bronze
P6832-3030K White
P6832-3130K Black
 Horizontal step/wall light.
 Wet location listed.
 2-7/8" ht., 4-1/2" W.
 5w LED module included.

STEP LIGHTS





P6802-31, P6803-31

P6802-31 Black
 Cast aluminum housing with black aluminum louver. For wood, brick, masonry, and poured concrete installations. IC Rated. Refer to diagram for size. One 7w 2-pin twin compact fluorescent lamp, G23 base.




P6803-30

P6803-31 Black
P6803-30 White
 Cast aluminum housing with metal louver. For wood, brick, masonry, and poured concrete installations. With Therma-Gard protection. Refer to diagram for size. One 25w 120V T6-1/2, intermediate base.



P6817-16

P6817-16 Satin Aluminum
P6817-31 Black
 Cast aluminum, tempered glass with louver faceplate. Two 1/2" I.P. for conduit entry. For poured concrete and masonry installations. Refer to diagram for size. One medium base, 25w max.




P6817-31

TRANSFORMERS

PLUG-IN COMPATIBLE TRANSFORMERS

- Multiple secondary taps of 12, 13 and 15 volts allow maximum light output and lamp life for long or short runs and loading variations (300, 600 and 900 watt units only)
- Three foot 12 gauge cord with grounding plug
- Thermal protection in the primary circuit to avoid overheating
- Resettable circuit breakers in secondary circuits for electrical safety and convenience
- Weatherproof construction, powder-coat painted (P8590-31, P8591-31, P8592-31, P8522-31 and P8523-31)
- Stainless steel construction (P8519-01, P8520-01 and P8521-01)
- Easy open enclosure with KO's for hardwiring and photocell installation
- Easy wire terminal board for secondary connections
- For outdoor use
- Plug in timer and photocell compatible, page 749



PRODUCT	WATT	DESCRIPTION	SIZE (W X H X D)
P8519-01	300	300w stainless steel	5-3/8" x 17" x 5-3/8"
P8520-01	600	(2) 300w circuits, stainless steel	6-5/8" x 17" x 5-5/8"
P8521-01	900	(3) 300w circuits, stainless steel	6-5/8" x 19" x 5-1/2"
P8522-31	300	300w	5-1/4" x 17" x 5-5/8"
P8523-31	600	(2) 300w circuits	6-1/2" x 17" x 5-5/8"

MANUAL TRANSFORMERS

- These transformers have all the features shown above except plug-in capability
- Powder coated for outdoor use
- Magnetic

PRODUCT	WATT	DESCRIPTION	SIZE (W X H X D)
P8590-31	150	150w magnetic manual	3-1/2" x 8-3/4" x 3"
P8591-31	300	300w magnetic manual	4" x 10-3/4" x 4-1/4"
P8592-31	600	(2) 300w magnetic circuits manual	4" x 12" x 4-1/2"



P8590-31, P8591-31, P8592-31

ELECTRONIC TRANSFORMERS

P8517-31 supplied with integral photo-cell. Non-metallic housing to prevent corrosion. Three foot 18-gauge cord with grounding plug. Suitable for outdoor installation only. 20w minimum.



P8518-31 supplied with remote mount photo-cell with auto setting and 2 hr., 6 hr., and 8 hr. shut off settings. Suitable for outdoor installation only. 20w minimum.

PRODUCT	WATT	DESCRIPTION	SIZE (W X H X D)
P8517-31	150	150w electronic	3-5/8" x 6-1/2" x 2-3/8"
P8518-31	300	300w electronic	5-1/8" x 7-1/4" x 2-3/4"

LED TRANSFORMER

P8270-31 Non metallic case protects timer controls and 120v to 12v transformer. Surge protected with grounded cord/plug set and easy 12V cable attachment. Photocontrol triggers "time on", eliminating seasonal adjustment. 56w max. Non-dimmable. Recommend using 14 gauge cable P8617 or P8626, page 749.



PRODUCT	WATT	DESCRIPTION	SIZE (W X H X D)
P8270-31	56	45w LED	4" x 5-5/8" x 3-1/2"

INSTALLATION ACCESSORIES

P8651-01 Black

Low voltage Quick-connector. Allows #10 or #12 gauge outdoor low voltage cable to connect to an 18 gauge wire from fixture. 1-5/8" W., 1-1/4" L., 5/8" ht.



P8671-31 Black

Polycarbonate canopy for tree trunks and walls. 1/2 NPS thread. Low voltage only. 4-1/4" dia. Extends 1-3/16".



P8672-31 Black

Miniature pedestal mount. Powder-coat painted cast metal. Flanged base for surface mounting. 1/2 NPS thread. Low voltage only. 1-1/2" dia., 1" ht.



P8708-01 Silicone filled

underground direct burial wire connector. #20-#10 gauge. 10 per pack (1 standard pack = 10 pieces). 1-5/8" L., 5/8" dia.



Mounting Stems 1/2 NPS threads

- 16" stem **P8666-31** Black
- P8666-38** Green
- 8" stem **P8667-31** Black
- P8667-38** Green



P8628-31 Black 12-gauge 100 ft.

P8699-31 Black 12-gauge 200 ft. 12-Volt Cable, 2 conductor. UL listed.



P8617-31 Black 14-gauge 75 ft.

P8626-31 Black 14-gauge 150 ft. Recommended for use with P8270-31 transformer and LED Lighting. Low voltage #14 cable runs from P8270-31 control center down path of lighting. UV protected, burial is not required, hide with mulch if desired. Perfect fit with fixture connectors for easy installation (150' is the max. run distance from transformer location to assure best fixture operation). Available in 75', P8617-31 and 150' lengths, P8626-31.



P8618-31 Black

Ground stake, 8-3/4" ABS movable stake for direct mounting of 12v landscape lights. 1/2 NPS thread.



P8562-31 Black

Quick-mount landscape post for 120v or 12v PVC. 3" dia., 20" length with stabilizing grid and post, 1/2 NPS threaded hole. Wet location listed.



PLUG-IN COMPATIBLE TRANSFORMER ACCESSORIES

P8524-01 Two-prong plug-in timer

2-3/4" W., 3-1/8" ht. Allows multiple settings. To be used with plug-in compatible transformers., page 748.



P8531-01 Digital timer

3"w, 4-1/8" ht, extends 1-5/8" Allows multiple settings. To be used with plug-in compatible transformers, page 748.



P8525-31 Direct mount photo-cell.

1-5/8" dia., 4-7/8" length. Turns transformer on at dusk and off when ambient light appears. To be used with plug-in compatible transformers, page 748.



P8526-31 Remote mount photo-cell.


1-3/8" dia., 5-1/4" length Turns on transformer at dusk and off when ambient light appears. Includes 10 ft. of cord. To be used with plug-in compatible transformers, page 748.



FLOOD/ACCENT LIGHT ACCESSORIES

P8613-31 Black

45° cube cell louver fits under supplied glass lens. 4-3/4" cube cell for P5235-31 & P5237-31.



P8614-31 Black

Light shields adjust to desired length on cowling of light fixture. Rotate bias-cut end to adjust cutoff angle. 7-1/4" long for P5235-31 & P5237-31.



LAMP

P7801-01 Lamp

18w T5 wedge base lamp.

