


PROGRESS[®]
LIGHTING



PRODUCT
SUPPLEMENT
JUNE 2016



CONTENTS

Turnbury	2
Spicewood	4
Trestle	4
Overbrook	5
Glimmer	6
Ratio	8
Mod	10
Pendants	12
Close-to-Ceiling	23
Sconces	26
Ceiling Fan Light Kits	27
Bath & Vanity	28
Outdoor	33
Index	37





Shown: P4760-141 four-light chandelier.

COASTAL-INSPIRED PIECES ARE POPULAR IN A VARIETY OF TODAY'S HOME DESIGNS. TURNBURY PENDANTS FEATURE A SOLID WOOD FRAME SURROUND WITH HAND-PAINTED, GALVANIZED METAL FITTINGS. THE DISTRESSED PINE FRAME FINISH IS REMINISCENT OF DRIFTWOOD THAT HAS BEEN WEATHERED IN THE SUN.

TURNBURY

FOUR-LIGHT CHANDELIER

P4760-141 Galvanized Finish
Size: 16" dia., 18-3/4" ht. Overall
ht. w/chain 93-1/2", wire 15'.
Lamps: Four candelabra base
lamps, each 60w max.

SIX-LIGHT CHANDELIER

P4761-141 Galvanized Finish
Size: 26" dia., 28-3/4" ht. Overall
ht. w/chain 103-1/2", wire 15'.
Lamps: Six candelabra base
lamps, each 60w max.

ONE-LIGHT MINI-PENDANT

P5317-141 Galvanized Finish
Size: 10" dia., 12-1/4" ht. Overall
ht. w/chain 87", wire 10'.
Lamp: One medium base lamp,
100w max.



P4760-141



P5317-141



P4761-141

*Fixtures shown with P7826-01 and
P7825-01 vintage lamps.*

THE STATEMENT-MAKING SPICEWOOD PENDANTS FEATURE A RICH, SOLID WOOD SURROUND IN A CLASSIC QUATREFOIL PATTERN. WROUGHT IRON METAL FITTINGS IN A GILDED IRON FINISH ARE PAIRED WITH A DISTRESSED PINE FRAME TO COMPLEMENT RUSTIC AND RECLAIMED DESIGN STYLES.

SPICEWOOD



FOUR-LIGHT CHANDELIER
P4766-71 Gilded Iron
 Size: 22" dia., 24-1/2" ht. Overall ht. w/chain 99-1/2", wire 15'.
 Lamps: Four candelabra base lamps, each 60w max.

SIX-LIGHT CHANDELIER
P4767-71 Gilded Iron
 Size: 30" dia., 32-1/2" ht. Overall ht. w/chain 107-1/2", wire 15'.
 Lamps: Six candelabra base lamps, each 60w max.

ONE-LIGHT MINI-PENDANT
P5318-71 Gilded Iron
 Size: 10" dia., 11" ht. Overall ht. w/stem 77", wire 10'.
 Lamp: One medium base lamp, 100w max.



TRESTLE

A HANDSOME LOOK FOR INDUSTRIAL OR RUSTIC LIVING SPACES. THE GILDED IRON FINISH IS ENHANCED BY HAND-PAINTED GOLDEN OAK ACCENTS.

ONE-LIGHT MINI-PENDANT
P5315-71 Gilded Iron
 Size: 7-7/8" dia., 14-3/4" ht. Overall ht. w/chain 88", wire 10'.
 Lamp: One medium base lamp, 60w max.



OVERBROOK FEATURES A SCROLLING FRAME SURROUNDING A SAILCLOTH TEXTURED SHADE IN A NATURAL LINEN FINISH. AVAILABLE IN AN ANTIQUE BRONZE OR A SILVER RIDGE FINISH.

OVERBROOK



THREE-LIGHT PENDANT

P5335-20 Antique Bronze

P5335-134 Silver Ridge

Size: 22" dia., 18-5/8" ht. Overall ht. w/stem 84", wire 15'.

Lamps: Three medium base lamps, each 75w max.

FOUR-LIGHT PENDANT

P5336-20 Antique Bronze

P5336-134 Silver Ridge

Size: 28" dia., 23-3/4" ht. Overall ht. w/stem 89", wire 15'.

Lamps: Four medium base lamps, each 75w max.



All stem-hung fixtures on this spread come with one 6" stem, four 12" stems and 6 links of chain.

ELEMENTS THAT SPARKLE CREATE AN INSTANT STATEMENT WITHIN THE HOME – GLIMMER FITS THE DEFINITION OF LIVABLE LUXURY. PRISMATIC GLASS PENDANTS ARE SUPPORTED BY AN ARCHITECTURALLY-STYLED FRAME IN SILVER RIDGE OR ANTIQUE BRONZE FINISHES.

GLIMMER

THREE-LIGHT SEMI-FLUSH CONVERTIBLE

P2325-20 Antique Bronze

P2325-134 Silver Ridge

Size: 13-1/8" dia., 15-1/2" ht.

Overall ht. w/chain 94", wire 10'.

Lamps: Three candelabra base lamps, each 60w max.



P2325-20



P2325-134

FIVE-LIGHT PENDANT

P5321-20 Antique Bronze

P5321-134 Silver Ridge

Size: 22-1/4" dia., 23-7/8" ht.

Overall ht. w/chain 99", wire 10'.

Lamps: Five candelabra base lamps, each 60w max.



P2325-20



P2325-134



P5321-134



P5321-20



P5320-20



P5320-134

THREE-LIGHT SEMI-FLUSH CONVERTIBLE

P2326-20 Antique Bronze
P2326-134 Silver Ridge
 Size: 16-1/4" dia., 19" ht. Overall ht. w/chain 96-1/2", wire 10'.
 Lamps: Three candelabra base lamps, each 60w max.

ONE-LIGHT MINI-PENDANT

P5320-20 Antique Bronze
P5320-134 Silver Ridge
 Includes one 6" stem, four 12" stems and 6 links of chain.
 Size: 6" dia., 11-1/4" ht. Overall ht. w/stem 77-1/2", wire 10'.
 Lamp: One medium base lamp, 100w max.



P2326-134



P2326-134



P2326-20



P2326-20

A SLEEK METAL FRAME SUPPORTS A LOW-SLUNG SHADE TO CREATE RATIO'S CASUAL MODERN STYLE. ALL FIXTURES INCLUDE A POLISHED GLASS DIFFUSER THAT OFFERS AN ELEGANT APPEAL AND IS EASIER TO CLEAN – OFFERING BOTH FASHION AND FUNCTION.

RATIO

THREE-LIGHT CONVERTIBLE

P3604-09 Brushed Nickel
P3604-20 Antique Bronze
Size: 16" dia., 11-1/2" ht. Overall ht. w/stem 77-1/2", wire 10'.
Lamps: Three medium base lamps, each 75w max.

FOUR-LIGHT PENDANT

P5015-09 Brushed Nickel
P5015-20 Antique Bronze
Size: 24" dia., 15-7/8" ht. Overall ht. w/stem 82", wire 10'.
Lamps: Four medium base lamps, each 75w max.

SIX-LIGHT PENDANT

P5021-09 Brushed Nickel
P5021-20 Antique Bronze
Size: 30" dia., 19-1/8" ht. Overall ht. w/stem 85", wire 10'.
Lamps: Six medium base lamps, each 75w max.





P5015-09



P5015-20



P5021-09



P5021-20

All Ratio fixtures come with one 6" stem, four 12" stems and 6 links of chain

GIVING A NOD TO THE SPACE AGE WITH MID-CENTURY MODERN APPEAL, MOD FEATURES A SLEEK LINEAR FRAME IN A POLISHED CHROME FINISH. CLEAR, SPHERICAL GLASS SHADES OFFER THE PERFECT FOCAL POINT FOR VINTAGE BULBS OR REFLECTOR-STYLE GLOBES.

MOD

ONE-LIGHT BATH

P2850-15 Polished Chrome
 Size: 5-7/8" W., 7-3/4" ht.
 Extends 7-3/8". H/CTR 3-7/8".
 Lamp: One candelabra base lamp,
 60w max.

TWO-LIGHT BATH

P2854-15 Polished Chrome
 Size: 15" W., 6-3/4" ht.
 Extends 7-3/8". H/CTR 2-3/8".
 Lamps: Two candelabra base
 lamps, each 60w max.

THREE-LIGHT BATH

P2856-15 Polished Chrome
 Size: 24" W., 6-3/4" ht.
 Extends 7-3/8". H/CTR 2-3/8".
 Lamps: Three candelabra base
 lamps, each 60w max.



P2857-15



P2856-15

FOUR-LIGHT BATH

P2857-15 Polished Chrome
 Size: 33" W., 6-3/4" ht.
 Extends 7-3/8". H/CTR 2-3/8".
 Lamps: Four candelabra base
 lamps, each 60w max.

FIVE-LIGHT CHANDELIER

P4755-15 Polished Chrome
 Size: 28-7/8" dia., 19-7/8" ht.
 Overall ht. w/stem 86", wire 15".
 Lamps: Five candelabra base
 lamps, each 60w max.

SIX-LIGHT CHANDELIER

P4756-15 Polished Chrome
 Size: 34" dia., 24-7/8" ht.
 Overall ht. w/stem 91", wire 15".
 Lamps: Six candelabra base
 lamps, each 60w max.



P2850-15



P2854-15



Shown: P4755-15 five-light chandelier.



P4755-15



P4756-15

Stem-hung fixtures come with one 6" stem, four 12" stems and 6 links of chain

Fixtures shown with P7826-01 vintage lamps.

PENN OFFERS A MODERN TAKE ON VINTAGE ELECTRIC DESIGN. TURNKEY DETAILS AND CLEAR GLASS GLOBES ARE ENHANCED BY A POLISHED NICKEL OR NATURAL BRASS FINISH.

PENN

THREE-LIGHT CHANDELIER

P4769-104 Polished Nickel

P4769-137 Natural Brass

Size: 22" dia., 17-3/4" ht. Overall ht. w/stem 84", wire 15'.

Lamps: Three medium base lamps, each 100w max.

ONE-LIGHT LARGE PENDANT

P5328-104 Polished Nickel

P5328-137 Natural Brass

Size: 12" dia., 15" ht. Overall ht. w/stem 81", wire 10'.

Lamp: One medium base lamp, 100w max.



CHRONICLE PENDANTS ADD VISUAL INTEREST AND ARE IDEAL FOR COMMERCIAL-STYLE HOME KITCHENS OR VINTAGE DINING AREAS. A METAL ACCENT RING ADDS A FINISHING TOUCH ON THE GLASS GLOBE. WHITE OPAL GLASS WITH POLISHED NICKEL FINISH OR CLEAR SEEDED GLASS WITH A BRONZE FRAME ARE AVAILABLE OPTIONS.

CHRONICLE



ONE-LIGHT MINI-PENDANT

P5309-20 Antique Bronze with clear seeded glass
P5309-104 Polished Nickel with white opal glass
Size: 8" dia., 9" ht. Overall ht. w/ stem 75", wire 10'.
Lamp: One medium base lamp, 100w max.

ONE-LIGHT PENDANT

P5311-20 Antique Bronze with clear seeded glass
P5311-104 Polished Nickel with white opal glass
Size: 12" dia., 13" ht. Overall ht. w/stem 79", wire 10'.
Lamp: One medium base lamp, 100w max.



Stem-hung fixtures come with one 6" stem, four 12" stems and 6 links of chain

Fixtures shown with P7825-01 vintage lamps.

STAUNTON



Shown: P5333-09, P5334-143 and P5504-20 pendants.



INSPIRED BY THE STACKED MODERN ELEMENTS OF ITEMS FOUND IN PARISIAN BOUTIQUES, STAUNTON'S CHESS PIECE SILHOUETTE OFFERS A SIGNATURE FOCAL POINT. AVAILABLE IN THREE SHAPES AND COLOR VARIATIONS – THEY CAN BE GROUPED AS A SINGLE STYLE OR MIXED AND MATCHED TO OFFER A MORE ECLECTIC LOOK. ALL PENDANTS FEATURE A VINTAGE, WOVEN CLOTH CORD.

ONE-LIGHT PENDANT

P5332-09 Brushed Nickel with clear glass
P5332-20 Antique Bronze with champagne glass
P5332-143 Graphite with smoked glass
 Size: 12" dia., 11-1/4" ht. Overall ht. w/cord 125-1/2"
 Lamp: One medium base lamp, 75w max.

ONE-LIGHT PENDANT

P5333-09 Brushed Nickel with clear glass
P5333-20 Antique Bronze with champagne glass
P5333-143 Graphite with smoked glass
 Size: 9" dia., 16-1/2" ht. Overall ht. w/cord 124", wire 10'.
 Lamp: One medium base lamp, 75w max.



ONE-LIGHT PENDANT

P5334-09 Brushed Nickel with clear glass
P5334-20 Antique Bronze with champagne glass
P5334-143 Graphite with smoked glass
 Size: 8 1/2" dia., 12-3/4" ht. Overall ht. w/cord 126-1/2", wire 10'.
 Lamp: One medium base lamp, 75w max.



Fixtures shown with P7825-01 vintage lamps.

REDISCOVER ANTIQUE NAUTICAL LANTERNS. BAY COURT CAN BE USED IN TRADITIONAL AND NON-TRADITIONAL FASHIONS AND IS AN IDEAL FIXTURE SHOWCASED AS A SINGLE PIECE OR IN MULTIPLES. ETCHED INTERIOR GLASS IS SURROUNDED BY WATER GLASS.

BAY COURT

ONE-LIGHT LARGE FOYER PENDANT

P5310-09 Brushed Nickel

P5310-20 Antique Bronze

Size: 15" dia., 18-5/8" ht. Overall ht. w/chain 93", wire 15'.

Lamp: One medium base lamp, 100w max.

See additional Bay Court fixtures in Progress Lighting Catalog 131.

P5310-09



P5310-20



ARCHIVES

THREE-LIGHT CHANDELIER W/IRON SHADE

P4768-20 Antique Bronze

P4768-81 Antique Nickel

Includes one 6" stem, four 12" stems and 6 links of chain

Size: 28" dia., 15-3/4" ht. Overall ht. w/stem 82", wire 15'.

Lamps: Three medium base lamps, each 60w max.

Shown with P7825-01 vintage lamps.

ARCHIVES FEATURES A CLASSIC VINTAGE STYLE. A TWO-TONED ANTIQUE BRONZE FINISH WITH SATIN BRASS ACCENTS OR ANTIQUE NICKEL FINISH WITH BRUSHED NICKEL ACCENTS ADD TO THE CHARM OF EARLY-ELECTRIC STYLE.

P4768-20



P4768-81



BEAKER HAS A HEIGHTENED SENSE OF MODERN INDUSTRIAL STYLING. AVAILABLE IN TWO STYLES, EACH WITH THEIR OWN UNIQUE CHARACTER. THESE VESSELS ARE SUSPENDED FROM HERRINGBONE CLOTH CORDS. AVAILABLE IN TWO FINISHES, HALF CLEAR, HALF MIRRORED GLASS WITH POLISHED CHROME FRAME OR CHAMPAGNE GLASS WITH ANTIQUE BRONZE FRAME.

BEAKER



ONE-LIGHT LED MINI-PENDANT

P5344-1530K9 Polished Chrome
 Size: 5" dia., 11-7/8" ht. Overall ht. w/chain 122"
 Lamp: One 3000K 9w integral LED module included. 623 source lumens, 90 CRI.



ONE-LIGHT LED MINI-PENDANT

P5345-2030K9 Antique Bronze
 Size: 10-1/4" dia., 11-1/2" ht. Overall ht. w/chain 121-1/2"
 Lamp: One 3000K 9w integral LED module included. 623 source lumens, 90 CRI.



ONE-LIGHT LED WALL SCONCE

P7117-1530K9 Polished Chrome
 Size: 4-3/4" W., 17" ht.
 Extends 9-1/8". H/CTR 4".
 Lamp: One 3000K 9w integral LED module included. 623 source lumens, 90 CRI.



ONE-LIGHT LED WALL SCONCE

P7125-2030K9 Antique Bronze
 Size: 10-1/4" W., 16-5/8" ht.
 Extends 11-7/8". H/CTR 4".
 Lamp: One 3000K 9w integral LED module included. 623 source lumens, 90 CRI.



LED fixtures are Title 24 compliant.
 See website for dimmer compatibility.

THE INDUSTRIAL FRAME IS FINISHED IN PAINTED GALVANIZED WITH METALLIC SILVER ACCENTS OR ANTIQUE BRONZE WITH VINTAGE BRASS TOUCHES. THE STRIKING FORM PROVIDES THE PERFECT ENCLOSURE FOR VINTAGE STYLE TUBULAR LAMPS.

INDUSTRIAL

MESH PENDANTS OFFER AN INTERWEAVING OPEN CAGE FRAME THAT CAN SERVE AS A FOCAL POINT IN ANY LIGHTING DESIGN.

MESH



ONE-LIGHT MINI-PENDANT

P5326-20 Antique Bronze
P5326-141 Galvanized Finish
 Size: 5" dia., 11-1/2" ht. Overall
 ht. w/cord 132-1/2", wire 10'.
 Lamp: One medium base lamp,
 60w max.

ONE-LIGHT PENDANT

P5327-20 Antique Bronze
P5327-141 Galvanized Finish
 Size: 6-1/4" dia., 14" ht. Overall
 ht. w/cord 135-1/2", wire 10'.
 Lamp: One medium base lamp,
 60w max.

ONE-LIGHT MINI-PENDANT

P5337-20 Antique Bronze
 Size: 8-1/2" dia., 8-3/8" ht. Overall
 ht. w/stem 74-1/2", wire 10'.
 Lamp: One medium base lamp,
 100w max.

ONE-LIGHT MINI-PENDANT

P5338-20 Antique Bronze
 Size: 8-1/2" dia., 8-3/8" ht. Overall
 ht. w/stem 74-1/2", wire 10'.
 Lamp: One medium base lamp,
 100w max.

P5327-20



P5338-20

P5326-20



P5326-141



P5327-20

P5327-141



P5337-20



Fixtures shown with P7827-01 vintage lamps.

FINN TAKES A NEW PERSPECTIVE ON AN OPEN CAGE DESIGN. THE BEAUTIFULLY GRAPHIC FRAME WRAPS AROUND AN ETCHED WHITE GLASS SHADE CREATING A FOCAL APERTURE FOR A SINGLE LAMP. AVAILABLE IN MATTE BLACK AND METALLIC SILVER FINISHES.

FINN



ONE-LIGHT PENDANT

P5324-31 Black

P5324-121 Metallic Silver

Size: 10" dia., 10-1/2" ht. Overall ht. w/stem 76-1/2", wire 10'.

Lamp: One medium base lamp, 100w max.

ONE-LIGHT LARGE PENDANT

P5325-31 Black

P5325-121 Metallic Silver

Size: 15" dia., 13-1/8" ht. Overall ht. w/stem 79", wire 10'.

Lamp: One medium base lamp, 100w max.



Stem-hung fixtures include one 6" stem, four 12" stems and 6 links of chain

INSPIRED TO ENHANCE MODERN HOME DECOR, DOME LED PENDANTS COME IN THREE INTRIGUING COLOR OPTIONS AND SIZES FOR FLEXIBLE LIGHTING DESIGNS WITHIN THE HOME. SATIN ALUMINUM AND GLOSS WHITE FINISHES FEATURES A SOFT SILVER INTERIOR SHADE WHILE THE ANTIQUE BRONZE DOME IS COMPLEMENTED WITH A PAINTED GOLD INTERIOR.

DOMES

LED MINI-PENDANT

P5340-1630K9 Satin Aluminum
P5340-2030K9 Antique Bronze
P5340-3030K9 White
 Size: 10" dia., 5-5/8" ht. Overall ht. w/cord 125-1/2"
 Lamp: One 3000K 9w integral LED module included. 623 source lumens, 90 CRI.



LED PENDANT

P5341-1630K9 Satin Aluminum
P5341-2030K9 Antique Bronze
P5341-3030K9 White
 Size: 16" dia., 8-7/8" ht. Overall ht. w/cord 129"
 Lamp: One 3000K 17w integral LED module included. 1211 source lumens, 90 CRI.



LED PENDANT

P5342-1630K9 Satin Aluminum
P5342-2030K9 Antique Bronze
P5342-3030K9 White
 Size: 22" dia., 11-3/4" ht. Overall ht. w/cord 131-1/2"
 Lamp: One 3000K 29w integral LED module included. 2197 source lumens, 90 CRI.



PARLAY HELPS FURTHER NAUTICAL-INSPIRED FASHION IN YOUR DECOR. THE TIERED SHADE SUPPORTS ETCHED GLASS TO OFFER ILLUMINATION AND TASK LIGHTING WHERE IT'S NEEDED. LED SOURCE OFFERS ENERGY EFFICIENCY, LONG LIFE AND AESTHETIC BENEFITS TO INTERIOR SPACES.

PARLAY



P5340-3030K9

LED MINI-PENDANT

P5329-0930K9 Brushed Nickel
P5329-1530K9 Polished Chrome
P5329-2030K9 Antique Bronze
 Size: 8" dia., 7-5/8" ht. Overall ht. w/stem 73-1/2"
 Lamp: One 3000K 9w integral LED module included. 623 source lumens, 90 CRI.



P5329-0930K9



P5340-2030K9



P5329-1530K9



P5340-1630K9



P5329-2030K9

Stem-hung fixtures include one 6" stem, four 12" stems and 6 links of chain

LED fixtures are Title 24 compliant. See website for dimmer compatibility.

TRADITIONAL DETAILS AND GRACEFUL LINES PROVIDE MODERN ELEGANCE TO ANY INTERIOR. CLASSIC FEATURES ETCHED GLASS SHADES WITH A CHROME, ANTIQUE BRONZE OR BRUSHED NICKEL FRAME.

CLASSIC



FIVE-LIGHT CHANDELIER

P4770-09 Brushed Nickel

P4770-15 Polished Chrome

P4770-20 Antique Bronze

Size: 21-7/8" dia., 17-1/4" ht.

Overall ht. w/chain 62", wire 96".

Lamps: Five medium base lamps, each 100w max.

FIVE-LIGHT CHANDELIER

P4757-09 Brushed Nickel

P4757-15 Polished Chrome

P4757-20 Antique Bronze

Size: 23" dia., 17-1/4" ht. Overall ht. w/chain 55-1/2", wire 15'.

Lamps: Five medium base lamps, each 100w max.



WITH SOPHISTICATED DESIGN
STYLING, JOY FEATURES
VOLUMINOUS CURVES FOR A SOFT
AND STYLISH PROFILE.

JOY



THREE-LIGHT SEMI-FLUSH CONVERTIBLE

P3864-09 Brushed Nickel
P3864-20W Antique Bronze
Size: 16-5/8" dia., 12-1/8" ht.
Overall ht. w/chain 51", wire 10".
Lamps: Three medium base
lamps, each 100w max.



THE EXPANDED MINGLE COLLECTION PROVIDES NUMEROUS OPTIONS, INCLUDING NEW PATTERNS AND SIZES FOR CEILING LIGHTING APPLICATIONS. THE EXISTING PATTERN OF ALTERNATING CIRCULAR SHAPES COMES IN TWO COLOR OPTIONS, ANTIQUE BRONZE WITH NATURAL PARCHMENT GLASS OR BRUSHED NICKEL WITH ETCHED PARCHMENT GLASS.

MINGLE LED



FLUSH MOUNT

P2318-0930K9 Brushed Nickel
P2318-2030K9 Antique Bronze
 Size: 11" dia., 5-7/8" ht.
 Lamp: One 3000K 17w integral LED module included. 1211 source lumens, 90 CRI.



SEMI-FLUSH MOUNT

P2320-0930K9 Brushed Nickel
P2320-2030K9 Antique Bronze
 Size: 14" dia., 10-1/2" ht.
 Lamp: One 3000K 17w integral LED module included. 1211 source lumens, 90 CRI.



FLUSH MOUNT

P2319-0930K9 Brushed Nickel
P2319-2030K9 Antique Bronze
 Size: 14" dia., 5-3/4" ht.
 Lamp: One 3000K 17w integral LED module included. 1211 source lumens, 90 CRI.



LED fixtures are Title 24 compliant.
 See website for dimmer compatibility.

THE ANTIQUE BRONZE LED FIXTURES FEATURE A GEOMETRIC PATTERN METAL FRAME SURROUNDING A SUMMER LINEN FABRIC SHADE WITH A GLASS DIFFUSER.

THE BRUSHED NICKEL LED FIXTURES FEATURE A MODERN SQUARE PATTERN THAT SURROUNDS A SUMMER LINEN FABRIC WITH GLASS DIFFUSER.

FLUSH MOUNT


P2327-2030K9 Antique Bronze
Size: 11" dia., 5-7/8" ht.
Lamp: One 3000K 17w integral LED module included. 1211 source lumens, 90 CRI.



P2327-2030K9

FLUSH MOUNT

P2328-2030K9 Antique Bronze
Size: 14" dia., 5-3/4" ht.
Lamp: One 3000K 17w integral LED module included. 1211 source lumens, 90 CRI.



P2328-2030K9

SEMI-FLUSH MOUNT

P2329-2030K9 Antique Bronze
Size: 14" dia., 10-1/2" ht.
Lamp: One 3000K 17w integral LED module included. 1211 source lumens, 90 CRI.



P2329-2030K9

FLUSH MOUNT

P2330-0930K9 Brushed Nickel
Size: 11" dia., 5-7/8" ht.
Lamp: One 3000K 17w integral LED module included. 1211 source lumens, 90 CRI.



P2330-0930K9

FLUSH MOUNT

P2331-0930K9 Brushed Nickel
Size: 14" dia., 5-3/4" ht.
Lamp: One 3000K 17w integral LED module included. 1211 source lumens, 90 CRI.



P2331-0930K9

SEMI-FLUSH MOUNT

P2332-0930K9 Brushed Nickel
Size: 14" dia., 10-1/2" ht.
Lamp: One 3000K 17w integral LED module included. 1211 source lumens, 90 CRI.



P2332-0930K9

ENJOY A STARRY NIGHT WITH BEYOND CEILING AND WALL MOUNT FIXTURES. THE DECORATIVE SHIELD FEATURES A PINHOLE PATTERN RESEMBLING A NIGHT SKY AND PROVIDES AN UNEXPECTED AND PLEASING "TWINKLE" EFFECT. AVAILABLE IN WALL MOUNT WITH A GENTLY CURVED METAL REFLECTOR FOR GRAZING EFFECT OR A GLASS DIFFUSER FOR CLOSE-TO-CEILING APPLICATIONS.

BEYOND



P3412-0930K9



LED FLUSH MOUNT

P2333-12930K9 Architectural Bronze

P2333-14330K9 Graphite

Size: 10-1/2" sq., Extends 3-1/4".
H/CTR 5-1/4".

Lamp: One 3000K 17w integral LED module included. 1211 source lumens, 90 CRI.

ADA



LED WALL SCONCE

P7101-12930K9 Architectural Bronze

P7101-14330K9 Graphite

Size: 10-1/2" sq., Extends 3-5/8".
H/CTR 5-1/4".

Lamp: One 3000K 17w integral LED module included. 1211 source lumens, 90 CRI.

ADA




FITTER

LED FLUSH MOUNT


P3412-0930K9 Brushed Nickel

Size: 11-1/2" dia., 5-3/4" ht.

Lamp: One 3000K 29w integral LED module included. 2800 source lumens, 90 CRI.



P7101-14330K9



P7101-12930K9



P2333-12930K9



P2333-14330K9

LED fixtures are Title 24 compliant.
See website for dimmer compatibility.

AS A MODERN EXTENSION TO THE PORTAL STYLE, THIS CONTEMPORARY CEILING LIGHT FEATURES A WHITE ACRYLIC LENS TO PROVIDE PLEASING ILLUMINATION. AVAILABLE IN BRUSHED NICKEL AND POLISHED CHROME FINISHES.

PORTAL

LED FLUSH MOUNT P3631-0930K9 BRUSHED NICKEL

P3631-0930K9 Brushed Nickel
P3631-1530K9 Polished Chrome
 Size: 9" dia., 2-1/2" ht.
 Lamp: One 3000K 17w integral LED module included. 1211 source lumens, 90 CRI.



P3631-0930K9



P3631-1530K9

LED FLUSH MOUNT

P3632-0930K9 Brushed Nickel
P3632-1530K9 Polished Chrome
 Size: 13" dia., 2-1/2" ht.
 Lamp: One 3000K lumen 29w integral LED module included. 2197 source lumens, 90 CRI.



P3632-0930K9



P3632-1530K9

AIRPRO®

UNIVERSAL STYLE LIGHT KITS WITH QUICK CONNECT WIRING.

LED CEILING FAN LIGHT KIT

P2659-09 Brushed Nickel
P2659-20 Antique Bronze
 Etched white glass.
 Size: 11-1/8" dia., 4" ht.
 Lamp: One 3000K 16.5w LED included. 1265 source lumens, 960 delivered lumens, 90 CRI.



P2659-09



P2659-20

LED CEILING FAN LIGHT KIT

P2660-09 Brushed Nickel
P2660-20 Antique Bronze
 Etched alabaster glass.
 Size: 11-1/4" dia., 5-3/8" ht.
 Lamp: One 3000K 16.3w LED included. 1241 source lumens, 1150 delivered lumens, 90 CRI.



P2660-09



P2660-20

METRIC



P2195-09



P2195-15

ONE-LIGHT BATH

P2193-09 Brushed Nickel

P2193-15 Polished Chrome

Size: 4-5/8" W., 8" ht.

Extends 5-1/4". H/CTR 4-1/8".

Lamp: One medium base lamp,
100w max.

THREE-LIGHT BATH

P2195-09 Brushed Nickel

P2195-15 Polished Chrome

Size: 22-1/8" W., 6-1/2" ht.

Extends 5-1/4". H/CTR 4-1/8".

Lamps: Three medium base
lamps, each 100w max.



P2193-09



P2193-15

Fixtures can be mounted up or down.

ENJOY A COOL MODERN DESIGN WITH METRIC. A SIMPLE, ETCHED OPAL GLASS SHADE NESTLES INSIDE A DIE-CAST FRAME THAT IS FINISHED IN EITHER POLISHED CHROME OR BRUSHED NICKEL – PROVIDING LIGHT ABOVE AND BELOW THE FIXTURE.

TWO-LIGHT BATH

P2194-09 Brushed Nickel
P2194-15 Polished Chrome
Size: 13" W., 6-1/2" ht.
Extends 5-1/4". H/CTR 4-1/8".
Lamps: Two medium base lamps, each 100w max.

FOUR-LIGHT BATH


P2196-09 Brushed Nickel
P2196-15 Polished Chrome
Size: 31-1/4" W., 6-1/2" ht.
Extends 5-1/4". H/CTR 4-1/8".
Lamps: Four medium base lamps, each 100w max.



P2194-15



P2194-09



P2196-15



P2196-09

MODERN ARCHITECTURAL STYLING FRAMES AN INTEGRATED LED SOURCE AND CIRCULAR ETCHED OPAL GLASS. FOR INCREASED DESIGN OPTIONS, FIXTURES CAN BE INSTALLED HORIZONTALLY OR VERTICALLY. FRAME BATH AND VANITY FIXTURE PROVIDES BEAUTIFUL AND CONTINUOUS ILLUMINATION, AS WELL AS ENERGY SAVING BENEFITS.

FRAME

LINEAR VANITY

P2781-0930K9 Brushed Nickel

P2781-12930K9 Architectural Bronze

Size: 12" W., 4-3/4" ht.

Extends 3-1/2". H/CTR 2-3/8".

Lamp: One 3000K 15w LED

included. 877 source lumens, 738 delivered lumens, 93 CRI.

LINEAR VANITY

P2782-0930K9 Brushed Nickel

P2782-12930K9 Architectural Bronze

Size: 24" W., 3 3/8" ht.

Extends 3-1/2". H/CTR 2-3/8".

Lamp: One 3000K 35w LED


included. 2250 source lumens, 1659 delivered lumens, 93 CRI.



P2781-0930K9



P2781-12930K9



P2782-0930K9



P2782-12930K9



P2781-0930K9



P2781-12930K9



P2782-0930K9



P2782-12930K9

A TUBULAR DESIGN Pairs WITH A GEOMETRIC BACK PLATE AND MESH ACCENTS TO CREATE TRUSS – A FIXTURE THAT CAN BE MOUNTED HORIZONTALLY OR VERTICALLY. CIRCULAR ETCHED OPAL GLASS CONTAINS AN INTEGRATED LED SOURCE TO PROVIDE A VARIETY OF ENERGY AND COST SAVINGS BENEFITS FOR THE HOMEOWNER. MODERN STYLE AND CONTINUOUS ILLUMINATION ARE IDEAL FOR A VARIETY OF BATH AND VANITY SETTINGS.

TRUSS

LINEAR VANITY

P2834-0930K9 Brushed Nickel

P2834-12930K9 Architectural Bronze

Size: 13" W., 4-3/4" ht.
Extends 3-7/8". H/CTR 2-3/8".
Lamp: One 3000K 20w LED included. 1084 source lumens, 737 delivered lumens, 93 CRI.

LINEAR VANITY

P2839-0930K9 Brushed Nickel

P2839-12930K9 Architectural Bronze

Size: 22-1/2" W., 4-3/4" ht.
Extends 3-7/8". H/CTR 2-3/8".
Lamp: One 3000K 35w LED included. 1954 source lumens, 1222 delivered lumens, 93 CRI.



P2834-0930K9




P2834-12930K9



P2839-12930K9

P2834-0930K9



P2839-0930K9



P2839-12930K9

LED fixtures are Title 24 compliant.
See website for dimmer compatibility.

RECTANGULAR ETCHED OPAL GLASS FIXTURE CAN BE INSTALLED VERTICALLY OR HORIZONTALLY TO ACCOMMODATE MODERN LIGHTING APPLICATIONS WITHIN THE BATH AND VANITY AREA. ENJOY BEAUTIFUL AND CONTINUOUS ILLUMINATION WITH WEDGE.

WEDGE



P2779-12930K9



P2779-1530K9



P2779-1530K9



P2779-12930K9

LINEAR VANITY

P2779-1530K9 Polished Chrome

P2779-12930K9 Architectural Bronze

Size: 10-1/2" W., 4-3/4" ht.
Extends 3-3/4". H/CTR 2-3/8".

Lamp: One 3000K 15w LED included. 1006 source lumens, 576 delivered lumens, 93 CRI.



P2780-12930K9

LINEAR VANITY

P2780-1530K9 Polished Chrome

P2780-12930K9 Architectural Bronze

Size: 22-1/2" W., 4-3/4" ht.
Extends 3-3/4". H/CTR 2-3/8".

Lamp: One 3000K 35w LED included. 2329 source lumens, 1845 delivered lumens, 90 CRI.



P2780-1530K9

*LED fixtures are Title 24 compliant.
See website for dimmer compatibility.*

MODERN GEOMETRIC OUTDOOR LED
SCONCES ARE DESIGNED TO COMPLEMENT
A RANGE OF RESIDENTIAL AND
COMMERCIAL ARCHITECTURAL STYLES. ADA
COMPLIANT. AVAILABLE IN BLACK, BRONZE
AND METALLIC GRAY FINISHES. DARK SKY
COMPLIANT.

CORNICE

LED OUTDOOR WALL SCONCE

P5634-2030K9 Antique Bronze

P5634-3130K9 Black

P5634-8230K9 Metallic Gray

Size: 5-1/4" W., 4-3/4" ht.

Extends 4". H/CTR 2-3/8".

Lamp: One 3000K 9w integral
LED module included. 623 source
lumens, 90 CRI.

ADA



P5634-2030K9



P5634-3130K9



P5634-8230K9

LED OUTDOOR WALL SCONCE

P5635-2030K9 Antique Bronze

P5635-3130K9 Black

P5635-8230K9 Metallic Gray

Size: 6-1/8" W., 5" ht.

Extends 4". H/CTR 2-3/8".

Lamp: One 3000K 9w integral
LED module included. 623 source
lumens, 90 CRI.

ADA



P5635-2030K9



P5635-3130K9



P5635-8230K9

THIS OUTDOOR LANTERN COLLECTION TAKES A MODERN APPROACH TO THE POPULAR PRAIRIE DESIGN STYLE. AVAILABLE IN ANTIQUE BRONZE WITH AMBER SEEDED GLASS OR BLACK WITH ETCHED SEEDED GLASS.

HAWTHORNE

ONE-LIGHT POST LANTERN

P5413-20 Antique Bronze
P5413-31 Black
 Size: 7-1/2" dia., 17-1/4" ht.
 Lamp: One candelabra base lamp, 60w max.

ONE-LIGHT SMALL HANGING LANTERN

P5513-20 Antique Bronze
P5513-31 Black
 Size: 5" dia., 9-1/8" ht. Overall ht. w/stem 74", wire 10'.
 Lamp: One medium base lamp, 100w max.

ONE-LIGHT LARGE HANGING LANTERN

P5523-20 Antique Bronze
P5523-31 Black
 Size: 7 1/2" dia., 14-7/8" ht.
 Overall ht. w/stem 88", wire 10'.
 Lamp: One medium base lamp, 100w max.

ONE-LIGHT SMALL WALL LANTERN

P5624-20 Antique Bronze
P5624-31 Black
 Size: 5" W., 9-5/8" ht.
 Extends 6-1/2". H/CTR 2-3/4".
 Lamp: One medium base lamp, 100w max.

ONE-LIGHT MEDIUM WALL LANTERN

P5625-20 Antique Bronze
P5625-31 Black
 Size: 6" W., 12-5/8" ht.
 Extends 8-3/8". H/CTR 3-3/8".
 Lamp: One medium base lamp, 100w max.

ONE-LIGHT LARGE WALL LANTERN

P5665-20 Antique Bronze
P5665-31 Black
 Size: 7 1/2" W., 16" ht.
 Extends 10-3/4". H/CTR 4-1/8".
 Lamp: One medium base lamp, 100w max.



Stem-hung fixtures include one 6" stem, four 12" stems and 6 links of chain



P5624-20

P5624-31



P5625-20

P5625-31



P5665-20



P5665-31

CLEAN LINES ARE UP FRONT AND CENTER FOR THESE MODERN LED OUTDOOR SCONCES. VALERA FEATURES A DIE-CAST ALUMINUM FRAME AND MATTE WHITE, ACRYLIC DIFFUSER. ENERGY EFFICIENT LED SOURCE OFFERS 3000K COLOR TEMPERATURE AND 90+CRI OUTPUT. FIXTURE IS AVAILABLE IN BRUSHED NICKEL AND ARCHITECTURAL BRONZE FINISHES. ADA.

VALERA LED

LED WALL LANTERN

P5800-0930K9 Brushed Nickel

P5800-12930K9 Architectural Bronze

Size: 5-5/8" W., 8" ht.

Extends 4". H/CTR 4".

Lamp: One 3000K 9w integral LED module included. 623 lumens, 90 CRI.

ADA



P5800-12930K9



P5800-0930K9

LED WALL LANTERN

P5801-0930K9 Brushed Nickel

P5801-12930K9 Architectural Bronze

Size: 8-5/8" W., 11" ht.

Extends 4". H/CTR 5-1/2".

Lamp: One 3000K 17w integral LED module included. 1211 lumens, 90 CRI.

ADA



P5801-0930K9



P5801-12930K9

LED WALL LANTERN

P5806-0930K9 Brushed Nickel

P5806-12930K9 Architectural Bronze

Size: 5-5/8" W., 16" ht.

Extends 4". H/CTR 8".

Lamps: Two 3000K 9w integral LED modules included. 623 lumens, each 90 CRI.

ADA



P5806-12930K9



P5806-0930K9

LED fixtures are Title 24 compliant. See website for dimmer compatibility.

ANDOVER

FOUR-LIGHT WALL LANTERN

P5627-20 Antique Bronze
 Size: 12-1/2" W., 34-1/4" ht.
 Extends 13-1/2". H/CTR 11-3/4".
 Lamps: Four candelabra base
 lamps, each 60w max.

*For additional Andover fixtures see
 Progress Lighting Catalog 131.*



P5627-20

A LARGER ADDITION TO THE ANDOVER COLLECTION, THIS LANTERN COMPLEMENTS GRAND SCALE HOMES WITH EITHER TRADITIONAL OR CONTEMPORARY ELEVATIONS. BEVELED GLASS PANELS ALLOW OPTIMUM BRIGHTNESS, WHILE HINGED DOOR PROVIDES FOR EASY RE-LAMPING.

INDEX

PRODUCT #	PG#		PG#		PG#
P2193	.28	P2839	.31	P5015	.8
P2194	.28	P2850	.11	P5021	.8
P2195	.29	P2854	.11	P5309	.13
P2196	.29	P2856	.11	P5310	.16
P2318	.24	P2857	.11	P5311	.13
P2319	.24			P5315	.4
P2320	.24	P3412	.26	P5317	.3
P2325	.6	P3604	.8	P5318	.4
P2326	.7	P3631	.27	P5320	.7
P2327	.25	P3632	.27	P5321	.6
P2328	.25	P3864	.23	P5324	.19
P2329	.25	P3864	.23	P5325	.19
P2330	.25			P5326	.18
P2331	.25	P4755	.10	P5327	.18
P2332	.25	P4756	.11	P5328	.12
P2333	.26	P4757	.22	P5329	.21
P2659	.27	P4760	.3	P5332	.15
P2660	.27	P4761	.3	P5333	.15
P2779	.32	P4766	.4	P5334	.14
P2780	.32	P4767	.4	P5335	.5
P2781	.30	P4768	.16	P5336	.5
P2782	.30	P4769	.12	P5337	.18
P2834	.31	P4770	.22	P5338	.18
				P5340	.20
				P5341	.20
				P5342	.20
				P5344	.17
				P5345	.17
				P5413	.34
				P5513	.34
				P5523	.34
				P5624	.35
				P5625	.35
				P5627	.37
				P5634	.33
				P5635	.33
				P5665	.35
				P5665	.34
				P5800	.36
				P5801	.36
				P5806	.36
				P7101	.26
				P7117	.17
				P7125	.17

Every effort has been made to ensure the accuracy of information in this catalog. Progress Lighting reserves the right to make product changes from time to time, without prior notification, which may change the information provided in this catalog. Errors brought to our attention will be corrected in subsequent issues.

UL Listed or Classified or CSA Certified unless otherwise noted.

Bulbs not included with fixtures unless specified. Specifications subject to change without notice.

Metal finishes not specified as "solid" have quality plated or painted finishes.

Finish representations are high resolution digital reproductions, and, while every effort has been made to render colors accurately, they may vary slightly from the actual product, especially hand-painted finishes, due to the nature of hand craftsmanship.

©Progress Lighting 2016
 All rights reserved.
 International Copyright Secured.

Progress Lighting

701 Millennium Boulevard
Greenville, South Carolina
29607

06/2016
progresslighting.com

PROGRESS[®]
LIGHTING

