



***sunlite***<sup>®</sup>

# Bulb Catalog

**LED** | 2017

For product inquiries or to place an order, please contact us at:

TOLL FREE PHONE: **800.605.BULB**

VISIT: **[www.sunlite.com](http://www.sunlite.com)**

For general information: **[info@sunlite.com](mailto:info@sunlite.com)**

Sales department: **[sales@sunlite.com](mailto:sales@sunlite.com)**

To request a catalog: **[catalog@sunlite.com](mailto:catalog@sunlite.com)**

#### **New York**

---

744 Clinton Street  
Brooklyn, NY 11231

t: 718.768.7000

f: 718.768.0970

#### **Florida**

---

3698 1/2 NW 16th Street Bay C  
Lauderhill, FL 33311

t: 954.316.6130

f: 954.316.6019

Use phone to  
scan QR code



or visit short URL at  
[sunlite.com/u/767351](http://sunlite.com/u/767351)



## A15 Appliance Bulbs

Household Appliances

- 300 Lumen
- 120 Volts
- 3000K Color Temperature
- 80 CRI
- ETL - Damp Location
- 6 Bulbs Per Case



1



2



3


Img#	Item#	Description	Watt	Eq. Watt	Color	Hours	Finish	Base	Dim
1	80134-SU	A15/LED/4.5W/D/CL/30K/CD	4.5	40	3000K	25000	Clear	Med (E26)	✓
2	80177-SU	A15/LED/4.5W/D/FR/30K/CD	4.5	40	3000K	25000	Frosted	Med (E26)	✓
3	80187-SU	A15/LED/4.5W/E14/D/FR/30K	4.5	40	3000K	25000	Frosted	Eur (E14)	✓

## A19 Household Bulbs

Standard A-Type

- 120 Volts
- Frosted Finish
- Medium (E26) Base
- UL Listed
- 12 Bulbs Per Case
- CRI 80
- Enclosed Fixture Use



Item#	Description	Watt	Eq. Watt	Color	Hours	Lumen		Dim
88330-SU	A19/LED/6W/E/D/27K	6	40	2700K	25000	480	✓	✓
88331-SU	A19/LED/6W/E/D/40K	6	40	4000K	25000	480	✓	✓
88332-SU	A19/LED/6W/E/D/50K	6	40	5000K	25000	480	✓	✓

# A19 Household Bulbs

60 Watt Equivalent Standard A-Type

- 10 Watt
- Frosted Finish
- Medium (E26) Base
- UL Listed - Damp Location
- CRI 80

**60 Watt  
Equivalent**



Card



Box



3 Pack

Item#	Description	Watt	Eq. Watt	Color	Hours	Lumen	LPW		Dim
Dimmable Enclosed Fixture Use		12 Case Qty							
80746-SU	A19/LED/10W/ES/D/27K	10	60	2700K	25000	800	80	✓	✓
88301-SU	A19/LED/10W/ES/D/30K	10	60	3000K	25000	800	80	✓	✓
80747-SU	A19/LED/10W/ES/D/40K	10	60	4000K	25000	800	80	✓	✓
80748-SU	A19/LED/10W/ES/D/50K	10	60	5000K	25000	800	80	✓	✓
Non-Dimmable		12 Case Qty							
80710-SU	A19/LED/10W/30K	10	60	3000K	20000	800	80	-	-
80735-SU	A19/LED/10W/30K/CD	10	60	3000K	20000	800	80	-	-
80736-SU	A19/LED/10W/50K/CD	10	60	5000K	20000	800	80	-	-
80737-SU	A19/LED/10W/65K/CD	10	60	6500K	20000	800	80	-	-
220 Volt		6 Case Qty							
80119-SU	A19/LED/10W/50K/220V	10	60	5000K	20000	800	80	-	-
3 Pack		6 Case Qty							
80730-SU	A19/LED/10W/30K/3PK	10	60	3000K	20000	800	80	-	-
80729-SU	A19/LED/10W/40K/3PK	10	60	4000K	20000	800	80	-	-
80731-SU	A19/LED/10W/50K/3PK	10	60	5000K	20000	800	80	-	-
80732-SU	A19/LED/10W/65K/3PK	10	60	6500K	20000	800	80	-	-



# A19 Household Bulbs

75 Watt Equivalent Standard A-Type

- 12 Watt
- 120 Volts
- Frosted Finish
- Medium (E26) Base
- UL Listed - Damp Location
- CRI 80

75 Watt  
Equivalent



Carded



3 Pack



Box



Item#	Description	Watt	Eq. Watt	Color	Hours	Lumen	LPW		Dim	
Dimmable Enclosed Fixture Use		12 Case Qty								
88305-SU	A19/LED/12W/ES/D/27K	12	75	2700K	25000	1100	91	✓	✓	
88306-SU	A19/LED/12W/ES/D/30K	12	75	3000K	25000	1100	91	✓	✓	
88307-SU	A19/LED/12W/ES/D/40K	12	75	4000K	25000	1100	91	✓	✓	
88308-SU	A19/LED/12W/ES/D/50K	12	75	5000K	25000	1100	91	✓	✓	
1 Pack		12 Case Qty								
Alternative Packaging	80820-SU	A19/LED/12W/D/30K	12	75	3000K	15000	1100	91	-	✓
	80823-SU	A19/LED/12W/D/30K/CD	12	75	3000K	15000	1100	91	-	✓
	80821-SU	A19/LED/12W/D/50K	12	75	5000K	15000	1100	91	-	✓
	80824-SU	A19/LED/12W/D/50K/CD	12	75	5000K	15000	1100	91	-	✓
	80822-SU	A19/LED/12W/D/65K	12	75	6500K	15000	1100	91	-	✓
	80825-SU	A19/LED/12W/D/65K/CD	12	75	6500K	15000	1100	91	-	✓
3 Pack		6 Case Qty								
80835-SU	A19/LED/12W/30K/3PK	12	75	3000K	15000	1100	91	-	-	
80834-SU	A19/LED/12W/40K/3PK	12	75	4000K	15000	1100	91	-	-	
80836-SU	A19/LED/12W/50K/3PK	12	75	5000K	15000	1100	91	-	-	
80837-SU	A19/LED/12W/65K/3PK	12	75	6500K	15000	1100	91	-	-	

# A19 Household Bulbs

100 Watt Equivalent Standard A-Type

- 120 Volts
- Frosted Finish
- Medium (E26) Base
- 80 CRI
- UL Listed - Damp Location
- CRI 80

**100 Watt Equivalent**



Carded



Box



3 Pack

Item#	Description	Watt	Eq. Watt	Color	Hours	Lumens	LPW		Dim
-------	-------------	------	----------	-------	-------	--------	-----	--	-----

Dimmable 12 Case Qty

Alternative Packaging

80826-SU	A19/LED/14W/D/30K	14	100	3000K	15000	1500	107	-	✓
80829-SU	A19/LED/14W/D/30K/ <b>CD</b>	14	100	3000K	15000	1500	107	-	✓
80827-SU	A19/LED/14W/D/50K	14	100	5000K	15000	1500	107	-	✓
80830-SU	A19/LED/14W/D/50K/ <b>CD</b>	14	100	5000K	15000	1500	107	-	✓
80828-SU	A19/LED/14W/D/65K	14	100	6500K	15000	1500	107	-	✓
80831-SU	A19/LED/14W/D/65K/ <b>CD</b>	14	100	6500K	15000	1500	107	-	✓

3 Pack 6 Case Qty

80838-SU	A19/LED/14W/30K/3PK	14	100	3000K	15000	1500	107	-	-
80846-SU	A19/LED/14W/40K/3PK	14	100	4000K	15000	1500	107	-	-
80839-SU	A19/LED/14W/50K/3PK	14	100	5000K	15000	1500	107	-	-
80840-SU	A19/LED/14W/65K/3PK	14	100	6500K	15000	1500	107	-	-


## A19 Household Bulbs

100 Watt Equivalent Standard A-Type

- 120 Volts
- Frosted Finish
- Medium (E26) Base
- UL Listed
- 12 Bulbs Per Case
- CRI 80
- Enclosed Fixture Use

100 Watt  
Equivalent



Item#	Description	Watt	Eq. Watt	Color	Hours	Lumen		Dim
80720-SU	A19/LED/15W/D/E/27K	15	100	2700K	25000	1600	✓	✓
80721-SU	A19/LED/15W/D/E/30K	15	100	3000K	25000	1600	✓	✓
80722-SU	A19/LED/15W/D/E/40K	15	100	4000K	25000	1600	✓	✓
80723-SU	A19/LED/15W/D/E/50K	15	100	5000K	25000	1600	✓	✓


## Omni-Directional A19 Household

270 Degrees of Light

- 120 Volts
- Frosted Finish
- Medium (E26) Base
- 80 CRI
- ETL Listed
- 6 Bulbs Per Case

270  
Degrees



Item#	Description	Watt	Eq. Watt	Color	Hours	Lumen		Dim
80740-SU	A19/LED/12W/ES/D/OD/27K	12	75	2700K	15000	1100	—	✓
80743-SU	A19/LED/12W/ES/D/OD/50K	12	75	5000K	15000	1100	—	✓
80742-SU	A19/LED/12W/ES/D/OD/65K	12	75	6500K	15000	1100	—	✓
80630-SU	A21/LED/13W/D/ES/OD/27K	13	75	2700K	15000	1100	—	✓




# GU24 Based A19 Household

60 Watt Equivalent Omni Directional

- 120 Volts
- Frosted Finish
- GU24 Base
- Dimmable
- ETL Listed
- 6 Bulbs Per Case

**60 Watt  
Equivalent**



Item#	Description	Watt	Eq. Watt	Color	Hours	Lumen	CRI	
88320-SU	A19/GU24/LED/10W/D/E/27K	10	60	2700K	15000	800	80	✓
88345-SU	A19/GU24/LED/10W/D/E/40K	10	60	4000K	15000	800	80	✓
88346-SU	A19/GU24/LED/10W/D/E/50K	10	60	5000K	15000	800	80	✓

# Colored A19

Party & Decoration

- 120 Volts
- Frosted Finish
- Medium (E26) Base
- UL Listed
- 12 Bulbs Per Case



Item#	Description	Watt	Color	Hours	Lumen	Dim	Wildlife
80145-SU	A19/3W/B/LED	3	Blue	25000	-	-	-
80146-SU	A19/3W/G/LED	3	Green	25000	-	-	-
80147-SU	A19/3W/O/LED	3	Orange	25000	-	-	✓
80148-SU	A19/3W/R/LED	3	Red	25000	-	-	✓
80149-SU	A19/3W/Y/LED	3	Yellow	25000	-	-	-
80168-SU	A19/3W/P/LED	3	Pink	25000	-	-	-



## Blacklight A19

UV Glowing Bulb

- 120 Volts
- Clear Finish
- Medium (E26) Base
- ETL Listed - Dry Location
- 12 Bulbs Per Case



Sunlite Exclusive!



Item#	Description	Watt	Color	Hours		Dim
80114-SU	A19/LED/2W/BLB	2	Black Light Blue	25000	-	-

## Blinking A19

Indicator

- 120 Volt
- 500 Lumens
- Frosted Finish
- Medium (E26) Base
- 80 CRI
- 12 Bulbs Per Case



Sunlite Exclusive!

Blinks On/Off

Item#	Description	Watt	Color	Hours		Dim
80204-SU	A19/LED/5W/BL/WW	5	3000K	25000	-	-



## G16 Globe

Decorative

- 25000 Hours Avg Rated Life
- 120 Volts
- Medium (E26) Base
- 80 CRI
- ETL Listed
- 6 Bulbs Per Case



Item#	Description	Watt	E. Watt	Color	Lumen	LPW	Finish		Dim
80518-SU	G16/LED/5W/D/E26/CL/ES/27K	5	40	2700K	350	70	Clear	✓	✓
80653-SU	G16/LED/5W/D/E26/FR/ES/27K	5	40	2700K	350	70	Frosted	✓	✓
80548-SU	G16/LED/7W/D/E26/CL/ES/27K	7	60	2700K	500	71	Clear	✓	✓
80549-SU	G16/LED/7W/D/E26/FR/ES/27K	7	60	2700K	500	71	Frosted	✓	✓

## G16.5 Globe Bulbs

Candelabra Based Decorative

- 25000 Hours Avg Rated Life
- 120 Volts
- Candelabra (E12) Base
- 80 CRI
- ETL Listed
- 6 Bulbs Per Case



Item#	Description	Watt	E. Watt	Color	Lumen	LPW	Finish		Dim
80409-SU	G16.5/LED/5W/D/E12/CL/ES/27K	5	40	2700K	350	70	Clear	✓	✓
80651-SU	G16.5/LED/5W/D/E12/FR/ES/27K	5	40	2700K	350	70	Frosted	✓	✓
80544-SU	G16.5/LED/7W/D/E12/CL/ES/27K	7	60	2700K	500	71	Clear	✓	✓
80545-SU	G16.5/LED/7W/D/E12/FR/ES/27K	7	60	2700K	500	71	Frosted	✓	✓

## G25 Globe Bulbs

Decorative

- 500 Lumen
- 15000 Hours Avg Rated Life
- 120 Volts
- Medium (E26) Base
- ETL Listed - Dry Location
- 6 Bulbs Per Case



Item#	Description	Watt	E. Watt	Color	Lumen	LPW	Finish		Dim
80671-SU	G25/LED/7W/D/CL/ES/27K	7	60	2700K	500	71	Clear	✓	✓
80673-SU	G25/LED/7W/D/FR/E/30K	7	60	3000K	500	71	Frosted	✓	✓
80672-SU	G25/LED/7W/D/FR/ES/27K	7	60	2700K	500	71	Frosted	✓	✓

# Chandelier

Decorative

- 25000 Hours Avg Rated Life
- 120 Volts
- 2700K Color Temperature
- ETL Listed
- >80 CRI
- 6 Bulbs Per Case
- 260 Degrees



1




2



3



4


Img#	Item#	Description	Watt	E. Watt	Color	Lumen	LPW	Finish		Dim
Torpedo Tip   Candelabra Base										
1	80770-SU	CTC/LED/4.5W/E12/CL/D/ES/27K	4.5	40	2700K	300	66	Clear	✓	✓
	80771-SU	CTF/LED/5W/E12/FR/D/ES/27K	4.5	40	2700K	300	66	Frosted	✓	✓
	80774-SU	CTC/LED/7W/E12/CL/D/ES/27K	7	60	2700K	500	71	Clear	✓	✓
	80405-SU	CTF/LED/7W/E12/FR/D/ES/27K	7	60	2700K	500	71	Frosted	✓	✓
Flame Tip   Candelabra Base										
2	80772-SU	CFC/LED/5W/E12/CL/D/ES/27K	4.5	40	2700K	300	66	Clear	✓	✓
	80773-SU	CFF/LED/5W/E12/FR/D/ES/27K	4.5	40	2700K	300	66	Frosted	✓	✓
	80776-SU	CFC/LED/7W/E12/CL/D/ES/27K	7	60	2700K	500	71	Clear	✓	✓
	80424-SU	CFF/LED/7W/E12/FR/DIM/ES/27K	7	60	2700K	500	71	Frosted	✓	✓
Torpedo Tip   Medium Base										
3	80780-SU	ETC/LED/5W/E26/CL/D/ES/27K	4.5	40	2700K	300	66	Clear	✓	✓
	80343-SU	ETF/LED/4.5W/E26/D/E/FR/27K	4.5	40	2700K	300	66	Frosted	✓	✓
	80790-SU	ETC/LED/7W/E26/CL/D/ES/27K	7	60	2700K	500	71	Clear	✓	✓
Flame Tip   Medium Base										
4	80479-SU	EFC/LED/5W/E26/CL/DIM/ES/27K	4.5	40	2700K	300	66	Clear	✓	✓
	80784-SU	EFC/LED/7W/E26/CL/D/ES/27K	7	60	2700K	500	71	Clear	✓	✓
	80477-SU	EFF/LED/7W/E26/FR/DIM/ES/27K	7	60	2700K	500	71	Frosted	✓	✓

## MR11 Reflector

Spotlight Bulb

- 12 Volts
- GU4 Base
- 6 Bulbs Per Case




Item#	Description	Watt	Color	Hours	Lumen	CRI		Dim
81002-SU	MR11/LED/3W/12V/D/30K	3	3000K	30000	240	80	-	✓

## MR16 Reflector

50 Watt Equivalent High Efficiency

- 12 Volts
- GU5.3 Base
- UL Listed
- 6 Bulbs Per Case
- Enclosed Fixture Use




Item#	Description	Watt	Color	Hours	Lumen	CRI		Dim
80885-SU	MR16/LED/7W/12V/FL40/D/E/27K	7	2700K	25000	550	80	✓	✓
80886-SU	MR16/LED/7W/12V/FL40/D/E/30K	7	3000K	25000	550	80	✓	✓
80887-SU	MR16/LED/7W/12V/FL40/D/E/40K	7	4000K	25000	550	80	✓	✓
80888-SU	MR16/LED/7W/12V/FL40/D/E/50K	7	5000K	25000	550	80	✓	✓

## MR16 Reflector

50 Watt Equivalent High Efficiency

- 12 Volts
- GU5.3 Base
- UL Listed
- 6 Bulbs Per Case



Item#	Description	Watt	Color	Hours	Lumen	CRI		Dim
80503-SU	MR16/LED/7W/FL35/D/CRI95/27K	7	2700K	25000	450	95	-	✓
80507-SU	MR16/LED/7W/FL35/D/CRI95/30K	7	3000K	25000	450	95	-	✓



## MR16 Reflector

- Clear Finish
- 75 CRI
- 120 Volt
- 12 Bulbs Per Case

120 Volt



Img#	Item#	Description	Watt	Color	Hours	Lumen	CRI		Dim
GU5.3 Base									
1	80096-SU	MR16/LED/2.2W/GU5.3/WW	2.2	3000K	30000	180	75	-	-
	80097-SU	MR16/LED/2.2W/GU5.3/W	2.2	6000K	30000	220	75	-	-
GU10 Base									
2	80302-SU	MR16/LED/2.8W/GU10/60K	2.8	6000K	30000	240	75	-	-
	80301-SU	MR16/LED/2.8W/GU10/WW	2.8	3300K	30000	240	75	-	-

## PAR16 Reflector GU10 Base

75 Watt Equivalent High Efficiency

- GU10 Base
- 120 Volts
- ETL Listed
- 6 Bulbs Per Case

COB Type



Item#	Description	Watt	Color	Hours	Lumen	CRI		Dim
80511-SU	PAR16/LED/7W/GU10/E/D/27K	7	2700K	25000	500	80	✓	✓
80512-SU	PAR16/LED/7W/GU10/E/D/30K	7	3000K	25000	500	80	✓	✓
80516-SU	PAR16/LED/7W/GU10/D/40K	7	4000K	25000	500	80	-	✓
80513-SU	PAR16/LED/7W/GU10/D/50K	7	5000K	25000	500	80	-	✓
80514-SU	PAR16/LED/7W/GU10/D/65K	7	6500K	25000	500	80	-	✓

## PAR16 Reflector Medium Base

75 Watt Equivalent High Efficiency

- Medium (E26) Base
- 120 Volts
- ETL Listed
- 6 Bulbs Per Case



Item#	Description	Watt	Color	Hours	Lumen	CRI		Dim
80122-SU	PAR16/LED/7W/D/E/27K	7	2700K	25000	500	80	✓	✓




## PAR20 Reflector

50 Watt Equivalent High Efficiency

- 25000 Hours Avg Rated Life
- 120 Volts
- Medium (E26) Base
- 82 CRI
- ETL Listed
- 6 Bulbs Per Case


COB Type



Item#	Description	Watt	Eq. Watt	Color	Lumen	LPW		Dim
80018-SU	PAR20/LED/6W/FL38/D/E/27K	6	50	2700K	450	75	✓	✓
80696-SU	PAR20/LED/6W/FL35/D/E/30K	6	50	3000K	450	75	✓	✓
80697-SU	PAR20/LED/6W/FL35/D/E/40K	6	50	4000K	450	75	✓	✓
80698-SU	PAR20/LED/6W/FL35/D/E/50K	6	50	5000K	450	75	✓	✓

## PAR30 Reflector

75 Watt Equivalent High Efficiency

Item#	Description	Watt	Eq. Watt	Color	Lumen	LPW		Dim
80875-SU	PAR30/LED/10W/FL35/D/E/27K	10	75	2700K	750	75	✓	✓
80876-SU	PAR30/LED/10W/FL35/D/E/30K	10	75	3000K	750	75	✓	✓
80877-SU	PAR30/LED/10W/FL35/D/E/40K	10	75	4000K	750	75	✓	✓
80878-SU	PAR30/LED/10W/FL35/D/E/50K	10	75	5000K	750	75	✓	✓

Long Neck

80880-SU	PAR30LN/LED/10W/FL40/D/E/27K	10	75	2700K	750	80	✓	✓
89234-SU	PAR30LN/LED/10W/FL40/D/E/30K	10	75	3000K	750	80	✓	✓
89232-SU	PAR30LN/LED/13.5W/FL40/D/E/40K	13.5	75	4000K	750	55	-	✓
80883-SU	PAR30LN/LED/10W/FL40/D/E/50K	10	75	5000K	750	80	✓	✓

## PAR38 Reflector

100 Watt Equivalent High Efficiency

Item#	Description	Watt	Eq. Watt	Color	Lumen	LPW		Dim
88340-SU	PAR38/LED/18W/FL40/D/E/27K	18	90	2700K	1500	83	*	✓

IP65 Rated

88326-SU	PAR38/LED/18W/FL40/D/E/30K	18	90	3000K	1500	83	*	✓
88325-SU	PAR38/LED/18W/FL40/D/E/40K	18	90	4000K	1500	83	*	✓
88327-SU	PAR38/LED/18W/FL40/D/E/50K	18	90	5000K	1500	83	*	✓
88328-SU	PAR38/LED/18W/FL40/D/E/65K	18	90	6500K	1500	83	*	✓

\* ES Pending

## High CRI PAR30 Reflector

90 CRI Series

- 40000 Hours Avg Rated Life
- Medium (E26) Base
- 120 Volt
- 90 CRI
- UL Listed
- 6 Bulbs Per Case



Item#	Description	Watt	Eq. Watt	Color	CRI	Lumen	LPW		Dim
88048-SU	PAR30/LED/10W/FL40/D/90/27K	10	75	2700K	90	750	75	-	✓
88049-SU	PAR30/LED/10W/FL40/D/90/30K	10	75	3000K	90	800	80	-	✓
Long Neck									
89008-SU	PAR30LN/LED/10W/FL40/D/E/90/30K	10	75	3000K	90	800	80	-	✓

## High CRI PAR38 Reflector

90 CRI Series

- 40000 Hours Avg Rated Life
- Medium (E26) Base
- 90 CRI
- UL Listed
- 6 Bulbs Per Case



Item#	Description	Watt	Eq. Watt	Color	CRI	Lumen	LPW		Dim
120-277 Multi Volt									
89094-SU	PAR38/LED/17W/FL40/90/MV/27K	17	120	2700K	90	1150	67	-	-
120 Volt									
88082-SU	PAR38/LED/17W/FL40/D/90/27K	17	120	2700K	90	1150	67	-	✓
88083-SU	PAR38/LED/17W/FL40/D/90/30K	17	120	3000K	90	1200	67	-	✓



Blue




Green



Red



Amber



Yellow



## Colored PAR20 Reflectors

- Medium (E26) Base
- 12 Bulbs Per Case

Item#	Description	Watt	Color	Hours	Volt	Dim	Wildlife
80001-SU	PAR20/LED/3W/B	3	Blue	25000	120	-	-
80002-SU	PAR20/LED/3W/G	3	Green	25000	120	-	-
80005-SU	PAR20/LED/2W/Y	2	Yellow	25000	120	-	-
80003-SU	PAR20/LED/2W/R	2	Red	25000	120	-	✓
80010-SU	PAR20/LED/2W/A	2	Amber	25000	120	-	✓

## Colored PAR30 Reflectors

Item#	Description	Watt	Color	Hours	Volt	Dim	Wildlife
80021-SU	PAR30/LED/4W/B	4	Blue	25000	120	-	-
80022-SU	PAR30/LED/4W/G	4	Green	25000	120	-	-
80025-SU	PAR30/LED/3W/Y	3	Yellow	25000	120	-	-
80023-SU	PAR30/LED/3W/R	3	Red	25000	120	-	✓
80033-SU	PAR30/LED/3W/A	3	Amber	25000	120	-	✓

## Colored PAR38 Reflectors

Item#	Description	Watt	Color	Hours	Volt	Dim	Wildlife
80041-SU	PAR38/LED/6W/B	6	Blue	25000	120	-	-
80042-SU	PAR38/LED/6W/G	6	Green	25000	120	-	-
80045-SU	PAR38/LED/4W/Y	4	Yellow	25000	120	-	-
80043-SU	PAR38/LED/4W/R	4	Red	25000	120	-	✓
80068-SU	PAR38/LED/4W/A	4	Amber	25000	120	-	✓

# PAR Reflectors

Damp Location Outdoor Series

- 120 Volts
- Medium (E26) Base
- 80 CRI
- Dimmable
- UL Listed
- 6 Bulbs Per Case



Wet Location

Img#	Item#	Description	Watt	Eq. Watt	Color	Lumen	Hours		Dim
PAR30									
1	88054-SU	PAR30/LED/14W/FL40/D/27K	14	75	2700K	800	40000	-	✓
PAR30 Long Neck									
2	88053-SU	PAR30L/LED/14W/FL40/D/27K	14	75	2700K	800	40000	-	✓
	88057-SU	PAR30L/LED/14W/FL40/D/30K	14	75	3000K	800	40000	-	✓
PAR38									
3	88063-SU	PAR38/LED/19W/FL40/D/27K	19	85	2700K	1000	40000	-	✓

# Colored PAR38

Colored Base

- 120 Volts
- Medium (E26) Base
- 80 CRI
- UL Listed
- 6 Bulbs Per Case

Wet Location



Item#	Description	Watt	Eq. Watt	Color	Lumen	Hours	Dim	Wildlife
80550-SU	PAR38/LED/8W/FL35/B	8	25	Blue	108	25000	-	-
80552-SU	PAR38/LED/8W/FL35/G	8	40	Green	400	25000	-	-
80558-SU	PAR38/LED/8W/FL35/Y	8	25	Yellow	106	25000	-	-
80556-SU	PAR38/LED/8W/FL35/R	8	25	Red	150	25000	-	✓
80554-SU	PAR38/LED/8W/FL35/O	8	25	Orange	124	25000	-	✓

## R14 Reflector

- 25000 Hours Avg Rated Life
- 120 Volts
- 2700k Color Temperature
- >80 CRI
- Frosted Finish
- ETL Listed - Dry Location
- 6 Bulbs Per Case



Img#	Item#	Description	Watt	Eq. Watt	Color	Base	Lumen		Dim
1	80430-SU	R14/LED/N/E17/4W/D/E/27K	4	25	2700K	Int (E17)	280	✓	✓
2	80431-SU	R14/LED/E26/4W/D/27K	4	25	2700K	Med (E26)	250	-	✓

## R20 Reflector

50 Watt Equivalent High Efficiency

- 560 Lumen
- 25000 Hours Avg Rated Life
- 120 Volts
- Frosted Finish
- Medium (E26) Base
- ETL Listed
- 6 Bulbs Per Case



Item#	Description	Watt	Eq. Watt	Color	Lumen	CRI		Dim
80051-SU	R20/LED/8W/D/ES/27K	8	50	2700K	560	80	✓	✓
80069-SU	R20/LED/8W/D/E/30K	8	50	3000K	560	80	✓	✓
80677-SU	R20/LED/8W/D/40K	8	50	4000K	560	80	-	✓
80678-SU	R20/LED/8W/D/50K	8	50	5000K	560	80	-	✓

## BR30 Reflector

High Efficiency

- 25000 Hours Avg Rated Life
- 120 Volts
- Frosted Finish
- Medium (E26) Base
- ETL - Damp Location
- 6 Bulbs Per Case




Item#	Description	Watt	Eq. Watt	Color	Lumen	LPW	CRI		Dim
81158-SU	BR30/LED/10W/D/E/27K	10	65	2700K	750	75	80	✓	✓
81155-SU	BR30/LED/10W/D/E/30K	10	65	3000K	750	75	80	✓	✓
81150-SU	BR30/LED/10W/D/E/40K	10	65	4000K	750	75	80	✓	✓
81156-SU	BR30/LED/10W/D/E/50K	10	65	5000K	750	75	80	✓	✓
81151-SU	BR30/LED/10W/D/65K	10	65	6500K	750	75	80	-	✓

## BR40 Reflector

High Efficiency

- 25000 Hours Avg Rated Life
- 120 Volts
- Frosted Finish
- Medium (E26) Base
- ETL Listed
- 6 Bulbs Per Case



Item#	Description	Watt	Eq. Watt	Color	Lumen	LPW	CRI		Dim
88080-SU	BR40/LED/13W/D/E/27K	13	75	2700K	950	73	80	✓	✓
81157-SU	BR40/LED/13W/D/E/30K	13	75	3000K	950	73	80	✓	✓
81152-SU	BR40/LED/13W/D/E/40K	13	75	4000K	950	73	80	✓	✓
81153-SU	BR40/LED/13W/D/50K	13	75	5000K	950	73	80	-	✓
89037-SU	BR40/LED/14W/D/65K	14	75	6500K	1060	75	80	-	✓





## Hospitality Series

Warm Dim

- 25000 Hours Avg Rated Life
- 120 Volts
- 3000K-1700K Color Temperature
- Frosted Finish
- Medium (E26) Base
- 80 CRI

DIM eco WARM

3000K 1700K



Img#	Item#	Description	Watt	Eq. Watt	Lumen	LPW	Dim
A19		12 Case Qty					
1	80500-SU	A19/LED/8W/DIM/WD/30-16K	8	40	700	87	✓
BR20		6 Case Qty					
2	80505-SU	BR20/LED/8W/DIM/WD/30-16K	8	50	650	81	✓
BR30		6 Case Qty					
3	80510-SU	BR30/LED/12W/DIM/WD/30-16K	12	65	1000	83	✓
BR40		6 Case Qty					
4	80515-SU	BR40/LED/20W/DIM/WD/30-16K	20	85	1600	80	✓

## Plant Growth Bulbs

- 120 Volt
- UL Listed - Damp Location



1



2



3



4

### Grow Light

Img#	Item#	Description	Watt	Hours	Base	Dimmable
A19						
1	88197-SU	A19/LED/PGL/9W	9	15000	Med (E26)	-
BR30						
2	88198-SU	BR30/LED/PGL/10W	10	25000	Med (E26)	✓
PAR38						
3	88199-SU	PAR38/LED/PGL/16.5W	16.5	25000	Med (E26)	✓
4' T8 Bypass   120-277 Volt						
4	88195-SU	T8/LED/PGL/4'/MV/18W/BYPASS	18	25000	Med Bi-Pin (G13)	-



## Tubular & Indicator Bulbs

- 50 Lumen
- 15000 Hours Avg Rated Life
- 120 Volts
- 2700K Color Temperature
- Clear Finish
- ETL - Damp Location
- 6 Bulbs Per Case



Img#	Item#	Description	Watt	Eq. Watt	Base	Dim	MOL	DIA
<b>Tubular</b>								
1	81072-SU	T5/LED/CL/1W/27K/E12/CD	1	10	Candelabra(E12)	-	-	1.7" 0.6"
	81071-SU	T6/LED/CL/1W/27K/E12/CD	1	10	Candelabra(E12)	-	-	1.8" 0.8"
2	81070-SU	T7/LED/CL/1W/27K/E17/CD	1	10	Intermediate(E17)	-	-	2.1" 0.9"
<b>Indicator</b>								
3	81065-SU	S6/LED/CL/1W/27K/E12/CD	1	10	Candelabra(E12)	-	-	1.9" 0.8"

## Indicator Bulb

Appliance & Decorative

- 50 Lumen
- 120 Volts
- Medium (E26) Base
- ETL - Damp Location
- 6 Bulbs Per Case



Item#	Description	Watt	Eq. Watt	Color	Hours	Finish	Dim
<b>Indicator Bulb</b>							
81069-SU	S11/LED/CL/1W/27K/E26/CD	1	10	2700K	15000	Clear	-
81068-SU	S11/LED/FR/1W/27K/E26/CD	1	10	2700K	15000	Frosted	-

## Colored Tubular

Sign & Indicator Bulbs


- 120 Volts
- 10 Bulbs Per Case



Item#	Description	Watt	Color	Hours	Finish	Dim
<b>Medium (E26) Base</b>						
80251-SU	T10/LED/1W/B	1	Blue	30000	White	-
80252-SU	T10/LED/1W/G	1	Green	30000	White	-
80253-SU	T10/LED/1W/R	1	Red	30000	White	-
80255-SU	T10/LED/1W/Y	1	Yellow	30000	White	-

## Colored Sign Bulbs

- 120 Volts
- Medium (E26) Base
- Transparent Colored Finish
- 20 Bulbs Per Case
- S14




Item#	Description	Watt	Color	Hours	Wildlife		Dim
80366-SU	S14/30LED/MED/A	1.1	Amber	50000	✓	-	-
80362-SU	S14/30LED/MED/B	1.7	Blue	30000	-	-	-
80363-SU	S14/30LED/MED/G	0.9	Green	30000	-	-	-
80364-SU	S14/30LED/MED/R	1.1	Red	30000	-	-	-
80361-SU	S14/30LED/MED/C	1.7	Clear	30000	-	-	-
80365-SU	S14/30LED/MED/Y	1.1	Yellow	30000	-	-	-
80333-SU	S14/LED/2W/CL/WW	2	Warm White	30000	-	-	-

## Sign Bulb

Appliance & Decorative

- 50 Lumen
- 120 Volts
- 2700K Color Temperature
- Medium (E26) Base
- 80 CRI
- ETL - Damp Location
- 6 Bulbs Per Case



Item#	Description	Watt	Eq. Watt	Hours	Finish		Dim
81067-SU	S14/LED/CL/1W/27K/E26/CD	1	10	15000	Clear	-	-
81066-SU	S14/LED/FR/1W/27K/E26/CD	1	10	15000	Frosted	-	-



## Colored MR16

- 75 CRI
- 12 Bulbs Per Case



Img#	Item#	Description	Watt	Color	Hours	Volt
JDR   Medium (E26) Base						
1	80194-SU	JDR/LED/2.8W/W	2.8	6500K	30000	120
	80195-SU	JDR/LED/2.8W/B	2.8	Blue	30000	120
	80196-SU	JDR/LED/2.8W/G	2.8	Green	30000	120
	80197-SU	JDR/LED/2.8W/R	2.8	Red	30000	120
	80198-SU	JDR/LED/2.8W/Y	2.8	Yellow	30000	120
MR16   GU5.3 Base						
2	80305-SU	MR16/LED/2W/GU5.3/12V/B	2	Blue	30000	12
	80308-SU	MR16/LED/2W/GU5.3/12V/G	2	Green	30000	12
	80309-SU	MR16/LED/2W/GU5.3/12V/R	2	Red	30000	12
	80317-SU	MR16/LED/2W/GU5.3/12V/Y	2	Yellow	30000	12
MR16   GU10 Base						
3	80326-SU	MR16/LED/2.8W/GU10/B	2.8	Blue	30000	120
	80327-SU	MR16/LED/2.8W/GU10/G	2.8	Green	30000	120
	80328-SU	MR16/LED/2.8W/GU10/R	2.8	Red	30000	120
	80329-SU	MR16/LED/2.8W/GU10/Y	2.8	Yellow	30000	120

## Multi-Colored MR16

Remote Change RGB

- White Finish
- GU5.3 Base
- 12 Bulbs Per Case
- Remote Control Included



Item#	Description	Watt	Hours	Lumen	Volt	Dim
80186-SU	MR16/LED/RGB/5W/12V	5	30000	90-110	12	✓

## Decorative Chandelier

### Colored Series

- 6 Bulbs Per Pack
- 20 Packs Per Case
- Crystal Design



Blue



Green



Red



Yellow



White

Item#	Description	Watt	Bulb	Color	Hours		Dim
<b>Candelabra (E12) Base</b>							
80700-SU	L3C7/LED/B/6PK	0.4	C7	Blue	50000	-	-
80701-SU	L3C7/LED/G/6PK	0.4	C7	Green	50000	-	-
80702-SU	L3C7/LED/R/6PK	0.4	C7	Red	50000	-	-
80704-SU	L3C7/LED/Y/6PK	0.4	C7	Yellow	50000	-	-
80703-SU	L3C7/LED/W/6PK	0.4	C7	White	50000	-	-
<b>Medium (E17) Base</b>							
80705-SU	L3C9/LED/B/6PK	0.4	C9	Blue	50000	-	-
80706-SU	L3C9/LED/G/6PK	0.4	C9	Green	50000	-	-
80707-SU	L3C9/LED/R/6PK	0.4	C9	Red	50000	-	-
80709-SU	L3C9/LED/Y/6PK	0.4	C9	Yellow	50000	-	-
80708-SU	L3C9/LED/W/6PK	0.4	C9	White	50000	-	-

## Colored Tubular

### Sign & Indicator Bulbs

- 120 Volts
- 10 Bulbs Per Case
- 2.3"(MOL) 1.3"(DIA)



Item#	Description	Watt	Color	Hours	Finish		Dim
<b>Candelabra (E12) Base</b>							
80256-SU	T10/LED/0.5W/C/B	0.5	Blue	30000	White	-	-
80268-SU	T10/LED/0.5W/C/G	0.5	Green	30000	White	-	-
80269-SU	T10/LED/0.5W/C/R	0.5	Red	30000	White	-	-
80272-SU	T10/LED/0.5W/C/Y	0.5	Yellow	30000	White	-	-



## G4 Bi-Pin

Halogen Replacement

- Bi-Pin (G4) Base
- 12 Volt
- 80 CRI



Clear

Frosted

Item#	Description	Watt	Color	Hours	Lumen	LPW	Dim	MOL	DIA
Clear <span style="float: right;">10 Case Qty</span>									
80861-SU	G4/LED/1.5W/CL/12V/D/30K/CD	1.5	3000K	25000	200	133	✓	1.5"	0.4"
Frosted <span style="float: right;">12 Case Qty</span>									
80802-SU	G4/LED/2.5W/12V/WW/CD	2.5	3000K	30000	200	80	—	2.4"	0.7"
80807-SU	G4/LED/2.5W/12V/W/CD	2.5	6000K	30000	220	88	—	2.4"	0.7"

## G9 Bi-Pin

Halogen Replacement

- Bi-Pin (G9) Base
- 80 CRI
- 120 Volts
- ETL Listed - Dry Location



1

2

3

Img#	Item#	Description	Watt	Color	Hours	Lumen	LPW	Dim	MOL	DIA
Frosted <span style="float: right;">10 Case Qty</span>										
1	80817-SU	G9/LED/2.5W/30K	2.5	3000K	30000	200	80	—	2.4"	0.7"
2	80816-SU	G9/LED/3W/30K	3	3000K	30000	270	90	✓	2.8"	1.2"
Clear <span style="float: right;">10 Case Qty</span>										
3	80865-SU	G9/LED/1.6W/CL/D/30K/CD	1.6	3000K	25000	200	125	✓	1.9"	0.6"
	80866-SU	G9/LED/2.5W/CL/D/30K	2.5	3000K	25000	280	112	✓	2.0"	0.6"

## Elevator Bulb 1383/GBF

Specialty

- 12 Volts
- Clear Finish
- 80 CRI
- 12 Bulbs Per Case



1383



GBF

Item#	Description	Watt	Color	Hours	Base	Lumen
<b>1383 Bulb</b>						
80307-SU	1383/1LED/3W/SC/12V/WW	3	3000K	30000	Single Contact Bayonet (BA15s)	120
<b>GBF Bulb</b>						
80375-SU	GBF/1LED/1.7W/DC/WW	1.7	3000K	30000	Double Contact Bayonet (BA15D)	95

## AR111 Aluminum Reflector

Spotlight Bulb

- 12 Volts
- G53 Base
- 80 CRI
- 12 Bulbs Per Case



Item#	Description	Watt	Eq. Watt	Color	Hours	Beam Angle	Lumen
81014-SU	AR111/LED/7W/30K/SP/12D	7	50	3000K	30000	12 (Spot)	600
81013-SU	AR111/LED/7W/30K/NFL/24D	7	50	3000K	30000	24 (Narrow Flood)	600
81012-SU	AR111/LED/7W/30K/FL/36D	7	50	3000K	30000	36 (Flood)	600




## Horizontal Instant Start Plug-In

PLD 4-Pin Ballast Dependable

- Plug and Play
- G24q Base 4 Pin
- 82 CRI
- UL Classified - Damp Location
- 12 Bulbs Per Case
- Ballast Required
- Replaces PLD 13-18-26 4 Pin
- Replaces PLT 26-32-42 4 Pin



G24q Base



Item#	Description	Watt	Replace	Color	Hours	Lumen	LPW	DLC	Dim
88260-SU	PLD/LED/7W/IS/30K	7	PLD 13	3000K	50000	650	95	-	-
88262-SU	PLD/LED/7W/IS/35K	7	PLD 13	3500K	50000	650	95	-	-
88264-SU	PLD/LED/7W/IS/40K	7	PLD 13	4000K	50000	700	100	✓	-
88268-SU	PLD/LED/9W/IS/30K	9	PLD 18	3000K	50000	850	95	✓	-
88270-SU	PLD/LED/9W/IS/35K	9	PLD 18	3500K	50000	850	95	✓	-
88272-SU	PLD/LED/9W/IS/40K	9	PLD 18	4000K	50000	900	100	✓	-
88274-SU	PLD/LED/9W/IS/50K	9	PLD 18	5000K	50000	900	100	✓	-


## Horizontal Bypass Plug-In

PLD 4-Pin Rewiring Required

- 120-277 Volts
- G24q Base 4 Pin
- 82 CRI
- UL Classified - Damp Location
- 12 Bulbs Per Case
- No Ballast Required
- Replaces PLD 13-18-26 4 Pin
- Replaces PLT 26-32-42 4 Pin



G24q Base




Item#	Description	Watt	Replace	Color	Hours	Lumen	LPW	DLC	Dim
88284-SU	PLD/LED/7W/30K	7	PLD 13	3000K	50000	650	95	-	-
88288-SU	PLD/LED/7W/40K	7	PLD 13	4000K	50000	700	100	-	-
88290-SU	PLD/LED/7W/50K	7	PLD 13	5000K	50000	700	100	-	-
88292-SU	PLD/LED/9W/30K	9.5	PLD 18	3000K	50000	850	90	-	-
88296-SU	PLD/LED/9W/40K	9.5	PLD 18	4000K	50000	900	95	-	-
88298-SU	PLD/LED/9W/50K	9.5	PLD 18	5000K	50000	900	95	-	-

## Vertical Instant Start Plug-In

Plug & Play

- G24q Base
- 82 CRI
- UL Classified
- 12 Bulbs Per Case
- Ballast Required




Item#	Description	Watt	Replace	Color	Hours	Lumen	LPW		Dim
88211-SU	PLV/E/LED/9W/IS/35K	9	PLD 26	3500K	50000	850	95	-	✓
88212-SU	PLV/E/LED/9W/IS/40K	9	PLD 26	4000K	50000	900	100	-	✓

## Linstra

Vanity Bulb

- 120 Volts
- 2700K Color Temperature
- S14s Base
- 80 CRI




Item#	Description	Watt	Replace	Color	Hours	Lumen	LPW		Dim
53149-SU	LN/LED/5W/D/27K/120V	5	LN 35	2700K	30000	420	84	-	✓
53150-SU	LN/LED/8W/D/27K	8	LN 60	2700K	30000	660	82	-	✓
53155-SU	LN/LED/16W/D/27K	16	LN 150	2700K	30000	1300	81	-	✓

## U Shaped T8

Instant Start

- Plug and Play
- 4000K Color Temperature
- 2G13 Base
- 82 CRI
- UL Listed
- 6 Bulbs Per Case



Item#	Description	Watt	Replace	Color	Hours	Lumen	LPW		Dim
87905-SU	T8/LED/U/12W/IS/40K	12	FB 32	4000K	50000	1800	150	-	-
87906-SU	T8/LED/U/17W/IS/40K	17	FB 32	4000K	50000	2200	129	-	-

# FT Lamps

Instant Start

- Plug and Play
- Frosted Finish
- 2G11 Base
- 82 CRI
- UL Listed
- 10 Bulbs Per Case
- 22.2"<sup>(MOL)</sup> 1.6"<sup>(DIA)</sup>



Item#	Description	Watt	Replace	Color	Hours	Lumens	LPW	DLC	Dim
81057-SU	FT/LED/23W/IS/30K	23	FT 40	3000K	50000	2800	121	-	-
81058-SU	FT/LED/23W/IS/35K	23	FT 40	3500K	50000	2800	121	-	-
81059-SU	FT/LED/23W/IS/40K	23	FT 40	4000K	50000	2800	121	-	-
81060-SU	FT/LED/23W/IS/50K	23	FT 40	5000K	50000	2800	121	-	-

# Bypass FT Lamps

Rewiring Required

- 4-Pin (2G11) Base
- 82 CRI
- UL Classified
- 10 Bulbs Per Case
- No Ballast Required
- 22.2"<sup>(MOL)</sup> 1.6"<sup>(DIA)</sup>



Item#	Description	Watt	Replace	Color	Hours	Lumen	LPW	DLC	Dim
81055-SU	FT/LED/23W/30K	23	FT 40	3000K	50000	2600	113	-	-
81056-SU	FT/LED/23W/40K	23	FT 40	4000K	50000	2800	121	-	-

# T8 Tubular

8 Foot Instant Start

- Plug and Play
- 82 CRI
- UL Listed
- 10 Bulbs Per Case



Img#	Item#	Description	Watt	Color	Hours	Lumen	LPW	DLC	Dim
8 Foot   RDC Base									
1	88245-SU	T8/LED/8'/42W/IS/HO	42	4000K	50000	5500	130	-	-
8 Foot   Single Pin (FA8) Base									
2	88240-SU	T8/LED/8'/33W/IS/40K	33	4000K	50000	4400	133	-	-
	88243-SU	T8/LED/8'/33W/IS/50K	33	5000K	50000	4400	133	-	-
	88241-SU	T8/LED/8'/33W/IS/65K	33	6500K	50000	4400	133	-	-

## T5 Tubular

Instant Start

- Mini Bi-Pin (G5) Base
- >82 CRI
- UL Listed
- 10 Bulbs Per Case
- Plug and Play
- Ballast Required



Item#	Description	Watt	Color	Hours	Lumen	LPW	Dim	DLC
<b>2 Foot</b>								
88220-SU	T5/LED/2'/11W/IS/30K	11	3000K	50000	1350	122	-	-
88221-SU	T5/LED/2'/11W/IS/40K	11	4000K	50000	1400	127	-	-
88222-SU	T5/LED/2'/11W/IS/50K	11	5000K	50000	1400	127	-	-
<b>4 Foot   G5 Base</b>								
88420-SU	T5/LED/4'/25W/IS/DLC/30K	25	5000K	3000K	3200	128	-	✓
88226-SU	T5/LED/4'/25W/IS/DLC/30K	25	3000K	50000	3200	128	-	✓
88421-SU	T5/LED/4'/25W/IS/DLC/40K	25	4000K	50000	3500	140	-	✓
88422-SU	T5/LED/4'/25W/IS/DLC/50K	25	5000K	50000	3500	140	-	✓
88423-SU	T5/LED/4'/25W/IS/65K	25	6500K	50000	3500	140	-	-

## T8 Tubular

Instant Start

- Plug and Play
- Medium Bi-Pin (G13) Base
- 82 CRI
- UL Listed
- 10 Bulbs Per Case
- Ballast Required
- 120-277 Volts



Item#	Description	Watt	Color	Hours	Lumen	LPW	Dim	DLC
<b>2 Foot   Bi-Pin Base</b>								
88400-SU	T8/LED/2'/8W/IS/DLC/30K	8	3000K	50000	1200	150	-	✓
88401-SU	T8/LED/2'/8W/IS/DLC/40K	8	4000K	50000	1250	156	-	✓
88402-SU	T8/LED/2'/8W/IS/DLC/50K	8	5000K	50000	1250	156	-	✓
88403-SU	T8/LED/2'/8W/IS/65K	8	6500K	50000	1250	156	-	-
<b>3 Foot   Bi-Pin Base</b>								
87960-SU	T8/LED/3'/11W/IS/30K	11	3000K	50000	1400	127	✓	-
87962-SU	T8/LED/3'/11W/IS/40K	11	4000K	50000	1450	131	✓	-



## T8 Tubular

Instant Start

- Plug and Play
- Medium Bi-Pin (G13) Base
- 82 CRI
- UL Listed
- 10 Bulbs Per Case
- Glass Tubes
- Ballast Required



Item#	Description	Watt	Color	Hours	Lumen	LPW	DLC
4 Foot							
88404-SU	T8/LED/4'/11.5W/IS/DLC/30K	11.5	3000K	50000	1700	147	✓
88405-SU	T8/LED/4'/11.5W/IS/DLC/40K	11.5	4000K	50000	1800	156	✓
88406-SU	T8/LED/4'/11.5W/IS/DLC/50K	11.5	5000K	50000	1800	156	✓
88090-SU	T8/LED/4'/12W/IS/30K	12	3000K	50000	1700	150	—
88074-SU	T8/LED/4'/14W/IS/50K	14	5000K	50000	1800	128	—
88408-SU	T8/LED/4'/15W/IS/DLC/30K	15	3000K	50000	2100	140	✓
88409-SU	T8/LED/4'/15W/IS/DLC/40K	15	4000K	50000	2200	146	✓
88410-SU	T8/LED/4'/15W/IS/DLC/50K	15	5000K	50000	2200	146	✓
88411-SU	T8/LED/4'/15W/IS/65K	15	6500K	50000	2200	146	—
4 Foot   Shatter Proof							
88181-SU	T8/LED/4'/14W/IS/SP/30K	14	3000K	50000	1800	128	—


## Bypass T8 Tubular

Rewiring Required

- Medium Bi-Pin (G13) Base
- >80 CRI
- UL Classified
- No Ballast Required
- 120-277 Volt



Item#	Description	Watt	Color	Hours	Lumen	LPW	DLC
2 Foot   Bi-Pin Base							
88034-SU	T8/LED/2'/9W/40K/DLC	9	4000K	50000	1150	127	✓
88035-SU	T8/LED/2'/9W/50K/DLC	9	5000K	50000	1150	127	✓
4 Foot   Bi-Pin Base							
88162-SU	T8/LED/4'/15W/DLC/30K	15	3000K	50000	1700	113	✓
88163-SU	T8/LED/4'/15W/DLC/40K	15	4000K	50000	1800	120	✓



# Advanced Bypass T8 Tubular


Ballast Removal Required

- >80 CRI
- UL Listed
- 120-277 Volt

**New Safe  
Wiring  
Instructions**



Sunlite's LED advance line utilizes proprietary Smart Switch technology, making installation 100% safe from accidental electric shock.



**INSTANT START** | **NO BALLAST REQUIRED** | **HIGH LUMEN PER WATT** | **120-277v MULTI-VOLT** | **MERCURY FREE** | **5 YEAR WARRANTY**

Item#	Description	Watt	Color	Hours	Lumen	LPW	DLC
<b>2 Foot   Medium Bi-Pin Base</b> <span style="float: right;">10 Case Qty</span>							
88430-SU	T8/LED/ADV/2'/9W/DLC/30K	9	3000K	50000	1100	122	✓
88431-SU	T8/LED/ADV/2'/9W/DLC/40K	9	4000K	50000	1150	127	✓
88432-SU	T8/LED/ADV/2'/9W/DLC/50K	9	5000K	50000	1150	127	✓
<b>4 Foot   Medium Bi-Pin Base</b> <span style="float: right;">10 Case Qty</span>							
88436-SU	T8/LED/ADV/4'/17W/DLC/30K	17	3000K	50000	2100	123	✓
88437-SU	T8/LED/ADV/4'/17W/DLC/40K	17	4000K	50000	2200	129	✓
88438-SU	T8/LED/ADV/4'/17W/DLC/50K	17	5000K	50000	2200	129	✓
<b>8 Foot   FA8 Base</b> <span style="float: right;">10 Case Qty</span>							
88440-SU	T8/LED/ADV/8'/43W/30K	43	3000K	50000	5020	116	-
88441-SU	T8/LED/ADV/8'/43W/40K	43	4000K	50000	5020	116	-
88442-SU	T8/LED/ADV/8'/43W/50K	43	5000K	50000	5020	116	-
88443-SU	T8/LED/ADV/8'/43W/65K	43	6500K	50000	5020	116	-

# Corn Cob Lamps

Super Bright

- 100-277 Volts
- >80 CRI
- UL Listed
- Non Dimmable
- Compatible with enclosed fixtures
- Recommended Use Without Ballast



**Mogul Adapter Included With All Medium Bases**

**Suitable For Enclosed Fixtures**

**Direct Line Voltage**

**IP65**

**HID Replacement Lamps**

Item#	Description	Watt	Color	Hours	Lumen	LPW	DLC	MOL	DIA
<b>Medium Base</b>									
80850-SU	CC/LED/15W/E26/MV/50K	15	5000K	50000	1950	130	—	6.7"	2.5"
80841-SU	CC/LED/19W/E26-E39/MV/50K	19	5000K	50000	2470	130	—	6.1"	2.5"
80842-SU	CC/LED/27W/E26-E39/MV/50K	27	5000K	50000	3645	135	—	7.4"	3.7"
80582-SU	CC/LED/54W/E26-E39/MV/AMBER	54	1700K-1900K	40000	4320	80	—	10.9"	3.5"
80570-SU	CC/LED/36W/E26-E39/MV/50K	36	5000K	40000	4320	120	—	8.9"	3.5"
80576-SU	CC/LED/45W/E26-E39/MV/50K	45	5000K	40000	5400	120	—	9.9"	3.5"
<b>Mogul Base</b>									
80583-SU	CC/LED/54W/E39/MV/50K	54	5000K	40000	5940	110	✓	11.0"	3.6"
80584-SU	CC/LED/75W/E39/MV/50K	75	5000K	40000	8250	110	✓	12.1"	3.7"
80844-SU	CC/LED/100W/E39/MV/50K	100	5000K	50000	14000	140	✓	12.8"	5.1"
80845-SU	CC/LED/125W/E39/MV/50K	125	5000K	50000	18400	147	✓	14.2"	5.1"

## UFO Fixtures

Colored Pendant Fixture

- Durable 3' Threaded Cord
- UL Listed



Item#	Description	Finish	W	H	D
80758-SU	CO/PD/BL	Blue	1.80"	42.00"	1.80"
80759-SU	CO/PD/PK	Pink	1.80"	42.00"	1.80"
80760-SU	CO/PD/WH	White	1.80"	42.00"	1.80"

## UFO Bulbs

Colored Pendant Bulbs

- 25000 Hours Avg Rated Life
- 120 Volts
- 3000K Color Temperature
- Medium (E26) Base
- 80 CRI
- UL Listed - Damp Location
- 6 Bulbs Per Case



Item#	Description	Watt	Eq. Watt	Hours	Finish	Lumen	MOL	DIA
80768-SU	UFO/LED/15W/30K/CH/ACRYLIC	15	75	25000	White/Silver	1100	2.6"	9.1"
80762-SU	UFO/LED/7W/30K/BBLUE	7	35	25000	Blue	550	2.5"	3.7"
80763-SU	UFO/LED/7W/30K/PINK	7	35	25000	Pink	550	2.5"	3.7"
80764-SU	UFO/LED/11W/30K/BBLUE	11	50	25000	Blue	800	2.6"	4.7"
80765-SU	UFO/LED/11W/30K/PINK	11	50	25000	Pink	800	2.6"	4.7"
80766-SU	UFO/LED/15W/30K/BBLUE	15	75	25000	Blue	1250	3.0"	8.3"
80767-SU	UFO/LED/15W/30K/PINK	15	75	25000	Pink	1250	3.0"	8.3"



# Star Filament

Decoration

- 120 Volts
- >75 CRI
- 2300K Color Temperature
- UL Listed



A19



Chandelier



S19



Globe



T10 Tubular

Item#	Description	Watt	Hours	Lumen	Finish	Base	MOL	DIA
Chandelier   Torpedo Tip <span style="float: right;">12 Case Qty</span>								
80129-SU	CTC/LED/SF/1W/CL/23K	1	20000	120	Clear	Candelabra (E12)	1.4"	3.6"
Victorian Style   A19 <span style="float: right;">12 Case Qty</span>								
80127-SU	A19/LED/SF/1.8W/CL/23K	1.8	20000	120	Clear	Medium (E26)	2.4"	4.3"
Edison Style   S19 <span style="float: right;">6 Case Qty</span>								
80128-SU	S19/LED/SF/1.8W/CL/23K	1.8	20000	120	Clear	Medium (E26)	2.5"	5.7"
Globes <span style="float: right;">6 Case Qty</span>								
80139-SU	G25/LED/SF/1.8W/CL/23K	1.8	20000	120	Clear	Medium (E26)	3.2"	4.5"
80153-SU	G30/LED/SF/1.8W/CL/23K	1.8	20000	120	Clear	Medium (E26)	5.7"	3.7"
80154-SU	G40/LED/SF/1.8W/CL/23K	1.8	20000	120	Clear	Medium (E26)	4.9"	6.7"
Tubular <span style="float: right;">24 Case Qty</span>								
80622-SU	T10/LED/SF/1.5W/CL/23K/128MM	1.5	20000	100	Clear	Medium (E26)	5.0"	1.2"
80624-SU	T10/LED/SF/2.4W/CL/23K/228MM	2.5	20000	140	Clear	Medium (E26)	8.9"	1.2"
80626-SU	T10/LED/SF/3W/CL/23K/300MM	3	20000	190	Clear	Medium (E26)	11.8"	1.2"

## Filament Style A19

LED Filament

- 120 Volts
- Clear Finish
- Medium (E26) Base
- UL/ETL Listed
- 6 Inner 24 Master Case Qty




Item#	Description	Watt	Eq. Watt	Color	Hours	Lumen	Dim
81108-SU	A19/LED/AQ/5W/D/CL/40K	5	40	4000K	15000	500	✓
81109-SU	A19/LED/AQ/5W/D/CL/50K	5	40	5000K	15000	500	✓
80456-SU	A19/LED/AQ/6W/D/CL/22K	6	25	2200K	15000	430	✓
80189-SU	A19/LED/AQ/6W/D/CL/27K	6	40	2700K	15000	600	✓
<b>Silverbowl</b>							
80497-SU	A19/LED/AQ/SB/6W/D/CL/22K	6	40	2200K	15000	540	✓

## Filament Style S19

LED Filament

- 120 Volts
- Clear Finish
- Medium (E26) Base
- Dimmable
- UL/ETL Listed
- 6 Bulbs Per Case



Filament	Item#	Description	Watt	Color	Hours	Lumen	Dim
1	80460-SU	S19/LED/AQ/3W/DIM/CL/22K	3	2200K	15000	240	✓
2	80150-SU	S19/LED/AQ/4W/DIM/CL/27K	4	2700K	15000	350	✓
3	80461-SU	S19/LED/AQ/6W/DIM/CL/22K/LONG	6	2200K	15000	600	✓
4	80890-SU	S19/LED/AQ/6W/DIM/CL/27K/LONG	6	2700K	15000	600	✓
5	80466-SU	S19/LED/AQ/8W/DIM/CL/22K/LONG	8	2200K	15000	600	✓
6	80602-SU	S19/LED/AQ/8W/CL/22K/LONG	8	2200K	15000	600	✓
7	80891-SU	S19/LED/AQ/8W/DIM/CL/27K/LONG	8	2700K	15000	800	✓

# Filament Style Torpedo Chandelier

Torpedo Tip LED Filament

- Clear Finish
- Candelabra (E12) Base
- 80 CRI
- UL/ETL Listed
- 6 Inner 24 Master Case Qty



Item#	Description	Watt	Eq. Watt	Color	Hours	Volt	Lumen		Dim
80646-SU	CTC/LED/AQ/4W/E12/D/CL/E/27K	4	40	2700K	15000	120	400	✓	✓
80446-SU	CTC/LED/AQ/4W/E12/D/CL/18K/CD2	4	25	1800K	15000	120	280	-	✓
80445-SU	CTC/LED/AQ/5W/E12/D/CL/27K	6	60	2700K	15000	220-277	630	-	-
80647-SU	CTC/LED/AQ/6W/E12/D/CL/E/27K	6	60	2700K	15000	120	600	✓	✓
81100-SU	CTC/LED/AQ/6W/E12/D/CL/30K	6	60	3000K	15000	120	600	-	✓
81101-SU	CTC/LED/AQ/6W/E12/D/CL/40K	6	60	4000K	15000	120	600	-	✓
80645-SU	CTC/LED/AQ/6W/E12/D/CL/50K	6	60	5000K	15000	120	600	-	✓



# Filament Style Chandelier

Torpedo Tip LED Filament

- 120 Volts
- Clear Finish
- Medium (E26) Base
- 80 CRI
- UL/ETL Listed



Item#	Description	Watt	Eq. Watt	Color	Hours	Lumen		Dim
80428-SU	ETC/LED/AQ/4W/E26/D/CL/27K/CD2	4	40	2700K	15000	350	-	✓
80649-SU	ETC/LED/AQ/6W/E26/D/CL/E/27K	6	60	2700K	15000	600	✓	✓
81106-SU	ETC/LED/AQ/6W/E26/D/CL/50K	6	60	5000K	15000	600	-	✓

# Filament Style Chandelier

Flame Tip LED Filament

- 15000 Hours Avg Rated Life
- 120 Volts
- Clear Finish
- 80 CRI
- UL/ETL Listed



1



2

Img#	Item#	Description	Watt	E. Watt	Color	Hours	Lumen		Dim
<b>Candelabra (E12) Base</b>									
1	80634-SU	CFC/LED/AQ/4W/E12/D/CL/27K	4	40	2700K	15000	400	-	✓
	80633-SU	CFC/LED/AQ/4W/E12/D/CL/27K/CD2	4	40	2700K	15000	400	-	✓
	80648-SU	CFC/LED/AQ/6W/E12/D/CL/E/27K	6	60	2700K	15000	600	✓	✓
	80447-SU	CFC/LED/AQ/4W/E12/D/CL/18K/CD2	4	25	1800K	15000	250	-	✓
	81104-SU	CFC/LED/AQ/6W/E12/D/CL/40K	6	60	4000K	15000	600	-	✓
	81105-SU	CFC/LED/AQ/6W/E12/D/CL/50K	6	60	5000K	15000	600	-	✓
<b>Medium (E26) Base</b>									
2	80449-SU	EFC/LED/AQ/4W/E26/D/CL/18K/CD2	4	25	1800K	15000	250	-	✓
	80421-SU	EFC/LED/AQ/4W/E26/D/E/CL/27K	4	40	2700K	15000	400	*	✓

\* ES Pending

# Filament Style Globes

Filament LED

- 120 Volts
- Clear Finish
- UL/ETL Listed



Img#	Item#	Description	Watt	Eq. Watt	Color	Hours	Lumen	Dim
G16   Medium (E26) Base								
1	80454-SU	G16/LED/AQ/3W/D/CL/22K	3	25	2200K	15000	250	✓
	81112-SU	G16/LED/AQ/3W/E26/D/CL/27K	3	25	2700K	15000	250	✓
G16.5   Candelabra (E12) Base								
	81125-SU	G16.5/LED/AQ/3W/E12/D/C	3	25	2700K	15000	250	✓
	81126-SU	G16.5/LED/AQ/3W/E12/D/C	3	25	3000K	15000	300	✓
	81127-SU	G16.5/LED/AQ/3W/E12/D/C	3	25	5000K	15000	330	✓
G25   Medium (E26) Base								
2	80464-SU	G25/LED/AQ/4W/D/CL/22K	4	25	2200K	15000	300	✓
	80465-SU	G25/LED/AQ/6W/D/CL/22K/LONG	6	35	2200K	15000	480	✓
	81115-SU	G25/LED/AQ/6W/D/CL/27K	6	75	2700K	15000	600	✓
	81116-SU	G25/LED/AQ/6W/D/CL/40K	6	75	4000K	15000	600	✓
	81117-SU	G25/LED/AQ/6W/D/CL/50K	6	75	5000K	15000	600	✓
	80494-SU	G25/LED/AQ/SB/6W/D/CL/27K	6	75	2700K	15000	400	✓
G30   Medium (E26) Base								
3	80450-SU	G30/LED/AQ/6W/D/CL/22K	6	40	2200K	15000	420	✓
	80600-SU	G30/LED/AQ/8W/CL/22K/LONG	8	100	2200K	15000	880	✓
	80601-SU	G30/LED/AQ/8W/CL/27K/LONG	8	100	2700K	15000	880	✓
G40   Medium (E26) Base								
	80463-SU	G40/LED/AQ/6W/D/CL/22K/LONG	6	75	2200K	15000	600	✓
	80467-SU	G40/LED/AQ/8W/D/CL/22K/LONG	8	75	2200K	15000	600	✓
	80472-SU	G40/LED/AQ/8W/D/CL/27K	8	100	2700K	15000	880	✓
	80444-SU	G40/LED/AQ/10W/DIM/CL/22K	10	100	2200K	15000	750	✓
Silver Bulb   Medium (E26) Base								
4	80506-SU	G40/LED/AQ/SB/7W/CL/27K	7	75	2700K	15000	600	✓



## Filament Style Sign

LED Filament

- 120 Volts
- Clear Finish
- Medium (E26) Base
- UL/ETL Listed



Item#	Description	Watt	Eq. Watt	Color	Hours	Lumen	Dim
80462-SU	S11/LED/AQ/3W/D/CL/22K	3	30	2200K	15000	240	✓
LU   Medium (E26) Base		10 Case Qty					
80616-SU	LU/LED/AQ/6W/CL/22K	6	40	2200K	15000	430	✓

## Designer Filament Style Sign

LED Filament

- 120 Volts
- UL/ETL Listed




Img#	Item#	Description	Watt	E. Watts	Color	Hours	Lumen	Dim	MOL	DIA
Diamond   Medium (E26) Base		12 Case Qty								
1	80469-SU	DIAMOND/LED/AQ/6W/D/CL/22K	6	40	2200K	15000	480	✓	6.4"	4.5"
2	80459-SU	FL/DIAMOND/LED/6W/D/AMBER/22K	6	40	2200K	15000	450	✓	6.3"	4.8"
G48 Swirl   Mogul (E39) Base		4 Case Qty								
3	80484-SU	G48/LED/SWIRL	10	100	2200K	15000	750	✓	8.6"	5.8"
4	80485-SU	CHIMNEY/LED/AQ/12W/DIM/22K	10	100	2200K	15000	750	✓	9.5"	5.9"

# Filament Style Tubular

LED Filament

- 120 Volts
- Clear Finish
- UL/ETL Listed



Img#	Item#	Description	Watt	Color	Hours	Lumen	Dim	MOL	DIA
T6.5 Tube   European (E17) Base 6 Case Qty									
1	81074-SU	T6/LED/AQ/2W/CL/E17/27K	2	2700K	15000	180	—	5.5"	0.8"
T6 Tube   Candelabra (E12) Base 12 Case Qty									
2	80453-SU	T6/LED/AQ/2W/E12/D/CL/27K/85MM	2	2700K	15000	120	✓	3.4"	0.8"
T8 Tube   Candelabra (E12) Base 12 Case Qty									
3	80457-SU	T8/LED/AQ/2W/E12/D/CL/22K/95MM	1.5	2200K	15000	150	✓	3.7"	1.0"
T8 Tube   Medium (E26) Base 10 Case Qty									
4	80489-SU	T8/LED/AQ/5W/D/CL/22K/	5	2200K	15000	450	✓	11.4"	1.0"
5	80482-SU	T8/LED/AQ/5W/D/CL/27K	5	2700K	15000	430	✓	8.5"	1.0"
T10 Tube   Medium (E26) Base 12 Case Qty									
6	80610-SU	T10/LED/AQ/2W/22K/CL/128MM	2	2200K	15000	160	✓	4.9"	1.2"
7	80612-SU	T10/LED/AQ/5W/22K/CL/128MM	6	2200K	15000	460	✓	4.9"	1.2"
8	80613-SU	T10/LED/AQ/5W/27K/CL/128MM	5	2700K	15000	430	—	5.0"	1.3"



Img#	Item#	Description	Watt	Color	Hours	Lumen	Dim	MOL	DIA
T10 Tube   Medium (E26) Base			12 Case Qty						
9	80614-SU	T10/LED/AQ/6W/22K/CL/221MM	6	2200K	15000	450	✓	8.9"	1.2"
T12 Tube   Medium (E26) Base			12 Case Qty						
10	80458-SU	T12/LED/AQ/3W/D/CL/22K	3	2200K	15000	240	✓	4.3"	1.5"
	80892-SU	T12/LED/AQ/3W/D/CL/27K	3	2700K	15000	350	✓	4.2"	1.5"
T12 Tube   Medium (E26) Base			10 Case Qty						
11	80488-SU	T12/LED/AQ/6W/D/CL/22K/X	6	2200K	15000	540	✓	12.2"	1.5"
T14 Tube   Medium (E26) Base   Amber Finish			12 Case Qty						
12	80606-SU	T14/LED/AQ/6W/22K/AMBER/107MM	6	2200K	15000	400	✓	4.3"	1.8"
13	80608-SU	T14/LED/AQ/6.5W/22K/AMBER/127MM	6.5	2200K	15000	400	✓	5.0"	1.8"

**sunlite**

# Don't let this be you on Shabbos.



[www.shabbulb.com](http://www.shabbulb.com)

- ▷ Item #81140-SU
- ▷ Manual Dimming
- ▷ Patent #9,541,262



## Be smart. Use Shabbulb.

The simple sliding lever allows you to completely reveal and conceal the light on Shabbos.

# TERMS & CONDITIONS

## **OPEN ACCOUNT**

New accounts are subject to approval. For credit applications, customers should submit a Sunlite credit application, and allow two weeks for processing. You will be notified accordingly.

## **PAYMENT TERMS**

Net 30 days subject to credit approval. All past due invoices are subject to a 2.5% interest charge, each month the invoice remains unpaid. C.O.D. A check must be presented to the courier upon delivery of all C.O.D. shipments. All C.O.D. fees are the responsibility of the customer. Drop shipment service is not available on C.O.D. orders.

## **MINIMUM ORDER**

There is a \$100 minimum order. Orders under \$100 will be charged a \$10 small order charge.

## **SPECIAL ORDER**

Special order are non-returnable and non-refundable. Once the order is confirmed, a special cannot be cancelled. Please take note of items that are a special order.

## **DAMAGES/SHORTAGES**

Claims for Shortage or shipments, must be claimed within 72 hours of receipt of the order. We regret we cannot issue credit for merchandise that has been damaged in transit. The responsibility of such damage(s) shall be taken by the carrier.

## **ADDING TO AN ORDER**

We will do our best to add to an existing order. However, if it's not possible, we will treat it as a new order and must comply with all terms of a new order.

## **BACK ORDERS**

All back orders will be shipped as soon as possible. If the customer has a "NO BACK ORDER POLICY", it must be communicated at the time the order is placed. If original order is subject to freight allowance, and backorder falls below minimum freight allowed, the back order shipment may be subject to freight charges.

## **CANCELING AN ORDER**

We will try to comply with your request to cancel an order. However, we can't be responsible for cancellations. Canceling an order may be subject to a restocking charge, depending on the status of the order in our system.

## **SHIPPING & DROP-SHIP**

We provide FREE delivery in the local N.Y. Tri-State area with minimum order. A charge will be applied to shipments delivered to a destination other than the customer's physical location for orders less than \$350. Any damages or additional standard fees (e.g. handling charge, re-delivery charge, etc...), are at the sole responsibility of the ordering customer.

## **FREIGHT**

All shipments are FOB Brooklyn, NY. Full freight is allowed on orders totaling \$1,000.00 or more for product delivering east of the Mississippi, and \$1,200.00 for orders delivering west of the Mississippi. Freight charges which were originally allowed, may be added to an outstanding invoice that is not paid within its allowed terms (usually 30 days). The freight allowance EXCLUDES any oversized boxes that are greater than four feet (i.e. 4 ft. fluorescent lamps, fixtures, etc...).

## **HANDLING FEES**

For all FedEx, UPS, USPS and other express services shipped on customer's personal accounts and 3rd party accounts, each order is subject to as much as a \$6.50 handling charge per box based on dimensional weight.

## **PACKAGING**

All packages are packed with great care using the best packing methods available. If damages occur in transit, "DO NOT REFUSE THE SHIPMENT." It will cause unnecessary shipping expenses and delays in your order. File a claim with the courier for the loss or damage. The courier is responsible for breakage during transit. We will try to assist you in collecting your claims for loss or damage.

## **RETURNS**

A written RMA must accompany all returns. A restocking charge may apply to all returned merchandise.

## **PRICES**

Prices are subject to change without any notice.

## **SPECIFICATIONS**

Due to the rapid advancement of LED technology, specifications are subject to change without notice.

## **PRODUCT & DESCRIPTIONS**

We are not responsible for any typographical errors.

## **SIZES & MEASUREMENTS**

All sizes and measurements are in inches, except where specified. Actual product sizes may vary.

## **WARRANTY**

Sunshine Lighting, Inc. (Sunlite) warrants most of our LED products for a period of one to five (1-5) years from the date of delivery (specific to the individual product warranty on the packaging or available at [www.sunlite.com](http://www.sunlite.com)) provided that said products have been installed and maintained in accordance with Sunlite's installation instructions. This warranty is limited to the repair or replacement of defective material or entire product and shall be determined at the discretion of the manufacturer as to what action is taken.

This warranty is limited to the product specifically and in no means warrants any incurred labor costs by any party involved.

Sunlite extends its warranty to the immediate buyer.

The immediate buyer must receive a Return Material Authorization (RMA) number prior to the return and the return must be visibly marked with the RMA number and the product must be returned (shipping prepaid) to Sunlite at 744 Clinton St. Brooklyn, NY. 11231.

The return must be within 30 days of receiving the RMA from Sunlite.

The warranty is subject to the following provisions:

A liability under this warranty is limited to free repair or replacement (at the manufacturers' discretion) of any operational defect and shall not extend to any other damages in connection to the misuse or mishandling of said product.

The warranty shall not apply to units which have not been handled in accordance with normal conditions of use, or units which have been subsequently processed or modified in any way, or units which have been subject to any damage affecting the overall operation of the Sunlite product.

Sunlite warranties on component parts of materials not manufactured by Sunlite may differ from the terms specified herein and will supersede Sunlite's warranty. The manufacturers' liability will also not apply in cases where defects are not reported within 30 days after they have become recognizable by the initial buyer or by the users of the product.

\*\*\*Building and safety codes vary widely throughout the world. Sunlite does not control nor will it be responsible for the selection of product supplied by others, configurations, or the installation of the product in a ceiling, wall or other area. Sunlite makes no other warranties or representation, either expressed or implied, concerning product fitness for a particular purpose. Sunlite will fabricate to dimensions shown on Sunlite supporting documentation but will not take responsibility for failure of submitting party(s) shop drawing dimensions against job site conditions. In no event will Sunlite be liable for direct, indirect, special or consequential damages including but not limited to loss of profit or use. Sunlite reserves the right to inspect or have returned all products alleged to be defective excluding shipping and handling costs. Sunlite makes no other warranty, expressed or implied, regardless of product. \*\*\*

Sunshine Lighting  
744 Clinton Street  
Brooklyn, NY 11231

