

LED Catalog

Lamps & Fixtures • Winter 2018



LITESPANLED®

selection. solutions. simplicity. eiko.com

Contents

LitespanLED® Replacement Lamps	2
HID Replacement Lamps.....	2
Linear Tubes.....	5
A19/A21 Replacement Lamps	9
Filament Dimmable Decorative Lamps	12
PL CFL Replacement Lamps.....	14
PLL Replacement Lamps.....	16
BR Replacement Lamps.....	17
PAR Replacement Lamps.....	18
MR Replacement Lamps	20
Decorative Replacement Lamps	22
G4 & G9 Replacement Lamps	23
LitespanLED® Fixtures.....	24
High Bay Fixtures	24
Linear Fixtures	26
Troffer & Panel Fixtures	28
Downlight Fixtures	30
Outdoor Fixtures.....	32
Wallpack Fixtures.....	34
Canopy Fixtures.....	36
LitespanLED® Miniature LED	38
Miniature LED.....	38
LitespanLED® Wire Rack Display Merchandiser.....	39
Ordering Information, Terms & Conditions	40



HID Replacement Lamps

- LED HID replacement lamps for high wattage HID fixtures
- Consumes a fraction of the energy of HID systems
- Lasts many times longer than HID
- Available in a wide range of wattages and sizes
- Eliminates maintenance costs for over 10 years
- State-of-the-art LED light sources deliver ultra-high lpw
- Medium base and mogul base styles available
- Choice of color temperatures

LitespanLED® HID Replacement Lamps

Order Code	Item	Lm	W	CCT	CRI	V	Life/Hrs L70	Base	Replaces HID	Photo #	DLC
09632	LED15WPT30KMED-G7	1,875	15W	3000K	80+	100~277V	50,000	E26	50W	1	
09390	LED15WPT40KMED-G7	1,875	15W	4000K	80+	100~277V	50,000	E26	50W	1	
09391	LED15WPT50KMED-G7	1,950	15W	5000K	80+	100~277V	50,000	E26	50W	1	
09633	LED19WPT30KMED-G7	2,375	19W	3000K	80+	100~277V	50,000	E26	75W	1	
09392	LED19WPT40KMED-G7	2,375	19W	4000K	80+	100~277V	50,000	E26	75W	1	
09393	LED19WPT50KMED-G7	2,470	19W	5000K	80+	100~277V	50,000	E26	75W	1	
09652	LED20WPT180/30KMED-G7	2,700	20W	3000K	80+	100~277V	50,000	E26	100W	2	
09653	LED20WPT180/40KMED-G7	2,700	20W	4000K	80+	100~277V	50,000	E26	100W	2	
09402	LED20WPT180/40KMOG-G7	2,700	20W	4000K	80+	100~277V	50,000	E39	100W	2	✓
09654	LED20WPT180/50KMED-G7	2,800	20W	5000K	80+	100~277V	50,000	E26	100W	2	
09403	LED20WPT180/50KMOG-G7	2,800	20W	5000K	80+	100~277V	50,000	E39	100W	2	✓
09634	LED24WPT30KMED-G7	3,000	24W	3000K	80+	100~277V	50,000	E26	100W	1	
09394	LED24WPT40KMED-G7	3,000	24W	4000K	80+	100~277V	50,000	E26	100W	1	
09395	LED24WPT50KMED-G7	3,120	24W	5000K	80+	100~277V	50,000	E26	100W	1	
09635	LED27WPT30KMED-G7	3,510	27W	3000K	80+	100~277V	50,000	E26	50-100W	3	
09636	LED27WPT30KMOG-G7	3,510	27W	3000K	80+	100~277V	50,000	EX39	50-100W	3	✓
09835	LED27WPT40KMED-347V-G7	3,240	27W	4000K	80+	347V	50,000	E26	125W	3	
09374	LED27WPT40KMED-G7	3,510	27W	4000K	80+	100~277V	50,000	E26	75W	3	
09829	LED27WPT40KMOG-347V-G7	3,240	27W	4000K	80+	347V	50,000	E39	125W	3	✓
09375	LED27WPT40KMOG-G7	3,510	27W	4000K	80+	100~277V	50,000	EX39	75W	3	✓
09836	LED27WPT50KMED-347V-G7	3,375	27W	5000K	80+	347V	50,000	E26	125W	3	
09376	LED27WPT50KMED-G7	3,645	27W	5000K	80+	100~277V	50,000	E26	75W	3	
09830	LED27WPT50KMOG-347V-G7	3,375	27W	5000K	80+	347V	50,000	E39	125W	3	✓
09377	LED27WPT50KMOG-G7	3,645	27W	5000K	80+	100~277V	50,000	EX39	75W	3	✓
09655	LED30WPT180/30KMED-G7	4,050	30W	3000K	80+	100~277V	50,000	E26	175W	2	

Continued on next page >>>



5 YEAR WARRANTY



LitespanLED® HID Replacement Lamps

Order Code	Item	Lm	W	CCT	CRI	V	Life/Hrs L70	Base	Replaces HID	Photo #	DLC
09656	LED30WPT/180/40KMED-G7	4,050	30W	4000K	80+	100~277V	50,000	E26	175W	2	
09404	LED30WPT/180/40KMOG-G7	4,200	30W	4000K	80+	100~277V	50,000	E39	175W	2	✓
09657	LED30WPT/180/50KMED-G7	4,200	30W	5000K	80+	100~277V	50,000	E26	175W	2	
09405	LED30WPT/180/50KMOG-G7	4,200	30W	5000K	80+	100~277V	50,000	E39	175W	2	✓
09637	LED36WPT30KMED-G7	4,860	36W	3000K	80+	100~277V	50,000	E26	100-150W	3	
09638	LED36WPT30KMOG-G7	4,860	36W	3000K	80+	100~277V	50,000	EX39	100-150W	3	✓
09837	LED36WPT40KMED-347V-G7	4,320	36W	4000K	80+	347V	50,000	E26	150W	3	
09378	LED36WPT40KMED-G7	4,860	36W	4000K	80+	100~277V	50,000	E26	100W	3	
09831	LED36WPT40KMOG-347V-G7	4,320	36W	4000K	80+	347V	50,000	E39	150W	3	✓
09379	LED36WPT40KMOG-G7	4,860	36W	4000K	80+	100~277V	50,000	EX39	100W	3	✓
09838	LED36WPT50KMED-347V-G7	4,500	36W	5000K	80+	347V	50,000	E26	150W	3	
09380	LED36WPT50KMED-G7	4,860	36W	5000K	80+	100~277V	50,000	E26	100W	3	
09832	LED36WPT50KMOG-347V-G7	4,500	36W	5000K	80+	347V	50,000	E39	150W	3	✓
09381	LED36WPT50KMOG-G7	4,860	36W	5000K	80+	100~277V	50,000	EX39	100W	3	✓
09658	LED40WPT/180/30KMED-G7	5,400	40W	3000K	80+	100~277V	50,000	E26	250W	2	
09659	LED40WPT/180/40KMED-G7	5,400	40W	4000K	80+	100~277V	50,000	E26	250W	2	
09406	LED40WPT/180/40KMOG-G7	5,600	40W	4000K	80+	100~277V	50,000	E39	250W	2	✓
09660	LED40WPT/180/50KMED-G7	5,600	40W	5000K	80+	100~277V	50,000	E26	250W	2	
09407	LED40WPT/180/50KMOG-G7	5,600	40W	5000K	80+	100~277V	50,000	E39	250W	2	✓
09639	LED45WPT30KMED-G7	5,850	45W	3000K	80+	100~277V	50,000	E26	150-175W	3	
09640	LED45WPT30KMOG-G7	5,850	45W	3000K	80+	100~277V	50,000	EX39	150-175W	3	✓
09839	LED45WPT40KMED-347V-G7	5,400	45W	4000K	80+	347V	50,000	E26	175W	3	
09382	LED45WPT40KMED-G7	5,850	45W	4000K	80+	100~277V	50,000	E26	150W	3	
09833	LED45WPT40KMOG-347V-G7	5,400	45W	4000K	80+	347V	50,000	E39	175W	3	✓
09383	LED45WPT40KMOG-G7	5,850	45W	4000K	80+	100~277V	50,000	EX39	150W	3	✓
09840	LED45WPT50KMED-347V-G7	5,625	45W	5000K	80+	347V	50,000	E26	175W	3	
09384	LED45WPT50KMED-G7	6,075	45W	5000K	80+	100~277V	50,000	E26	150W	3	
09834	LED45WPT50KMOG-347V-G7	5,625	45W	5000K	80+	347V	50,000	E39	175W	3	✓
09385	LED45WPT50KMOG-G7	6,075	45W	5000K	80+	100~277V	50,000	EX39	150W	3	✓
09641	LED54WPT30KMED-G7	7,020	54W	3000K	80+	100~277V	50,000	E26	150-175W	3	
09642	LED54WPT30KMOG-G7	7,020	54W	3000K	80+	100~277V	50,000	EX39	150-175W	3	✓
09386	LED54WPT40KMED-G7	7,020	54W	4000K	80+	100~277V	50,000	E26	175W	3	
09428	LED54WPT40KMOG-347V-G7	7,020	54W	4000K	80+	347V	50,000	E39	175W	3	✓
09387	LED54WPT40KMOG-G7	7,020	54W	4000K	80+	100~277V	50,000	EX39	175W	3	✓
09388	LED54WPT50KMED-G7	7,290	54W	5000K	80+	100~277V	50,000	E26	175W	3	
09450	LED54WPT50KMOG-347V-G7	7,290	54W	5000K	80+	347V	50,000	E39	175W	3	✓
09389	LED54WPT50KMOG-G7	7,290	54W	5000K	80+	100~277V	50,000	EX39	175W	3	✓
09827	LED80WPT40KMOG-347V-G8	10,400	80W	4000K	80+	347V	50,000	E39	250W	4	✓
09346	LED80WPT40KMED-G6	10,400	80W	4000K	80+	100~277V	50,000	EX39	250W	4	✓
09828	LED80WPT50KMOG-347V-G8	10,800	80W	5000K	80+	347V	50,000	E39	250W	4	✓
09347	LED80WPT50KMED-G6	10,400	80W	5000K	80+	100~277V	50,000	EX39	250W	4	✓
09661	LED100WPT30KMOG-G6	12,000	100W	3000K	80+	100~277V	50,000	EX39	400W	4	
09451	LED100WPT40KMOG-347V-G7	12,000	100W	4000K	80+	347V	50,000	E39	250W	4	
09825	LED100WPT40KMOG-347V-G8	13,000	100W	4000K	80+	347V	50,000	E39	400W	4	✓
09348	LED100WPT40KMED-G6	13,000	100W	4000K	80+	100~277V	50,000	EX39	400W	4	✓
09452	LED100WPT50KMOG-347V-G7	12,500	100W	5000K	80+	347V	50,000	E39	250W	4	
09826	LED100WPT50KMOG-347V-G8	13,500	100W	5000K	80+	347V	50,000	E39	400W	4	✓
09349	LED120WPT40KMOG-G6	15,600	120W	4000K	80+	100~277V	50,000	EX39	600W	4	✓
09154	LED120WPT50KMOG-G6	15,960	120W	5000K	80+	100~277V	50,000	EX39	600W	4	✓



LitespanLED® Area Light HID Replacement Lamps

Order Code	Item	Lm	W	CCT	CRI	V	Life/Hrs L70	Base	Replaces HID	Photo #	DLC
09643	LED80WAL30KMOG-G7	10,400	80W	3000K	80+	100~277V	50,000	EX39	400W	5	✓
09644	LED80WAL40KMOG-G7	10,400	80W	4000K	80+	100~277V	50,000	EX39	400W	5	✓
09645	LED80WAL50KMOG-G7	10,800	80W	5000K	80+	100~277V	50,000	EX39	400W	5	✓
09646	LED110WAL30KMOG-G7	14,300	110W	3000K	80+	100~277V	50,000	EX39	600W	5	✓
09647	LED110WAL40KMOG-G7	14,300	110W	4000K	80+	100~277V	50,000	EX39	600W	5	✓
09648	LED110WAL50KMOG-G7	14,850	110W	5000K	80+	100~277V	50,000	EX39	600W	5	✓

LitespanLED® Temporary Work Light

Order Code	Item	Lm	W	CCT	CRI	V	Life/Hrs L70	Base	Replaces HID	Photo #	DLC
09649	TMP-3C-50K-U	6,900	60W	5000K	80+	120V	50,000	Hook	250W	6	✓
09650	TMP-4C-50K-U	9,200	80W	5000K	80+	120V	50,000	Hook	320W	6	✓
09651	TMP-5C-50K-U	11,500	100W	5000K	80+	120V	50,000	Hook	400W	6	✓

LitespanLED® Highbay HID Replacement Lamps

Order Code	Item	Lm	W	CCT	CRI	V	Life/Hrs L70	Base	Replaces HID	Photo #	DLC
10097	LED75WHB50KMOG-G8	9,000	75W	5000K	80+	100~277V	50,000	EX39	400W	N/A	
09698	LED115WB40KMOG-G7	14,950	115W	4000K	80+	100~277V	50,000	EX39	400W	7	✓
09699	LED115WB50KMOG-G7	15,525	115W	5000K	80+	100~277V	50,000	EX39	400W	7	✓
10098	LED120WHB50KMOG-G8	15,000	120W	5000K	80+	100~277V	50,000	EX39	400W	N/A	





Linear Tubes

- Solid state replacement for T5, T8 and T12 linear fluorescent
- Available in line voltage/ballast bypass, direct fit, and hybrid dual mode for a range of installation options
- Ultra-high performance LEDs deliver exceptional lpw
- Available in shatterproof nano-polycarbonate and PET-coated versions
- NSF Listed for commercial foodservice equipment

LitespanLED® T8 Dual Mode Replacement Lamps

Order Code	Item	Length	Lm	Nominal Lamp W	V (Ballast Dependent)	CCT	CRI	Bm	Life/Hrs L70	Photo #	DLC
09517	LED15WT8F/48/835K-G7DM	4'	1,800	15W	120~277V	3500K	80+	220°	50,000	1	
09291	LED15WT8F/48/840K-G7DM	4'	1,800	15W	120~277V	4000K	80+	220°	50,000	1	
09292	LED15WT8F/48/850K-G7DM	4'	1,800	15W	120~277V	5000K	80+	220°	50,000	1	

LitespanLED® T8 Direct Fit Replacement Lamps

Order Code	Item	Length	Lm	Nominal Lamp W	V (Ballast Dependent)	CCT	CRI	Bm	Life/Hrs L70	Photo #	DLC
60440	LED8WT8/24/835-G7DR	2'	1,200	8W	120~277V	3500K	80+	220°	50,000	1	✓
60441	LED8WT8/24/840-G7DR	2'	1,250	8W	120~277V	4000K	80+	220°	50,000	1	✓
60442	LED8WT8/24/850-G7DR	2'	1,250	8W	120~277V	5000K	80+	220°	50,000	1	✓
09785	LED10.5WT8F/36/835-G7DR	3'	1,400	11W	120~277V	3500K	80+	220°	50,000	1	
09786	LED10.5WT8F/36/840-G7DR	3'	1,450	11W	120~277V	4000K	80+	220°	50,000	1	
09787	LED10.5WT8F/36/850-G7DR	3'	1,450	11W	120~277V	5000K	80+	220°	50,000	1	
60443	LED11.5WT8/48/835-G7DR	4'	1,700	12W	120~277V	3500K	80+	220°	50,000	1	✓
09562	LED11.5WT8/48/835-PET-G7DR	4'	1,700	12W	120~277V	3500K	80+	220°	50,000	1	✓
60444	LED11.5WT8/48/840-G7DR	4'	1,800	12W	120~277V	4000K	80+	220°	50,000	1	✓
09563	LED11.5WT8/48/840-PET-G7DR	4'	1,800	12W	120~277V	4000K	80+	220°	50,000	1	✓
09564	LED11.5WT8/48/850-PET-G7DR	4'	1,800	12W	120~277V	5000K	80+	220°	50,000	1	✓
09931	LED12WT8/48/835-G8DR	4'	1,700	12W	120~277V	3500K	80+	220°	50,000	1	✓
09932	LED12WT8/48/840-G8DR	4'	1,800	12W	120~277V	4000K	80+	220°	50,000	1	✓
09933	LED12WT8/48/850-G8DR	4'	1,800	12W	120~277V	5000K	80+	220°	50,000	1	✓
09559	LED15WT8/48/835-G7DR	4'	2,100	15W	120~277V	3500K	80+	220°	50,000	1	✓

Continued on next page >>>



LitespanLED® T8 Direct Fit Replacement Lamps

Order Code	Item	Length	Lm	Nominal Lamp W	V (Ballast Dependent)	CCT	CRI	Bm	Life/Hrs L70	Photo #	DLC
09934	LED15WT8/48/835-G8DR	4'	2,100	15W	120~277V	3500K	80+	220°	50,000	2	✓
09672	LED15WT8/48/835-PET-G7DR	4'	2,100	15W	120~277V	3500K	80+	220°	50,000	1	✓
09935	LED15WT8/48/840-G8DR	4'	2,200	15W	120~277V	4000K	80+	220°	50,000	2	✓
09936	LED15WT8/48/850-G8DR	4'	2,200	15W	120~277V	5000K	80+	220°	50,000	2	✓
09673	LED15WT8/48/840-PET-G7DR	4'	2,200	15W	120~277V	4000K	80+	220°	50,000	1	✓
09561	LED15WT8/48/850-G7DR	4'	2,200	15W	120~277V	5000K	80+	220°	50,000	1	✓
09674	LED15WT8/48/850-PET-G7DR	4'	2,200	15W	120~277V	5000K	80+	220°	50,000	1	✓
09167	LED18T8F/48/835-G6DR	4'	1,800	14W	120~277V	3500K	80+	220°	50,000	1	
09168	LED18T8F/48/840-G6DR	4'	1,800	14W	120~277V	4000K	80+	220°	50,000	1	
09355	LED22T8F/48/835-G6DR	4'	2,100	17W	120~277, 347V	3500K	80+	210°	50,000	1	
09302	LED22T8F/48/835-G6DR-M*	4'	2,100	17W	120~277V	3500K	80+	220°	50,000	1	
09290	LED22T8F/48/840-G6DR-M*	4'	2,200	17W	120~277V	4000K	80+	220°	50,000	1	

*Canada only.

LitespanLED® T8 Direct Fit U-Bend


Order Code	Item	Length	Lm	Nominal Lamp W	V (Ballast Dependent)	CCT	CRI	Bm	Life/Hrs L70	Photo #	DLC
10063	LED11.5WT8F/U6/840-G8DR	2'	1,800	11.5W	120~277V	4000K	82+	220°	50,000	3	
09113	LED18T8F/U6/835-G5DR	2'	1,800	12W	120~277V	3500K	82+	220°	50,000	3	
09114	LED18T8F/U6/840-G5DR	2'	1,800	12W	120~277V	4000K	82+	220°	50,000	3	
09116	LED18T8F/U6/850-G5DR	2'	1,800	12W	120~277V	5000K	82+	220°	50,000	3	
60458	LED12WT8/U1/835-G7DR	2.24"	1,700	13W	120~277V	3500K	82+	220°	50,000	4	
60459	LED12WT8/U1/840-G7DR	2.24"	1,800	13W	120~277V	4000K	82+	220°	50,000	4	
60460	LED12WT8/U1/850-G7DR	2.24"	1,800	13W	120~277V	5000K	82+	220°	50,000	4	

LitespanLED® T8 Linear Bypass/Line Voltage U-Bend

Order Code	Item	Length	Lm	W	V	CCT	CRI	Bm	Life/Hrs L70	Photo #	DLC
09789	LED15WT8F/U6/835-G7D	22.44"	1,700	15W	120~277V	3500K	80+		50,000	3	✓
09790	LED15WT8F/U6/840-G7D	22.44"	1,800	15W	120~277V	4000K	80+		50,000	3	✓
09791	LED15WT8F/U6/850-G7D	22.44"	1,800	15W	120~277V	5000K	80+		50,000	3	✓

LitespanLED® Bypass/Line Voltage Nano Polycarbonate

Order Code	Item	Length	Lm	W	V	CCT	CRI	Bm	Life/Hrs L70	Photo #	DLC
09368	LED9WT8/P/24/835-G7D	2'	1,100	9W	120~277V	3500K	80+	210°	50,000	5	✓
09369	LED9WT8/P/24/840-G7D	2'	1,150	9W	120~277V	4000K	80+	210°	50,000	5	✓
09370	LED9WT8/P/24/850-G7D	2'	1,150	9W	120~277V	5000K	80+	210°	50,000	5	✓
09736	LED14WT8/P/48/835-G8D	4'	1,700	14W	120~277V	3500K	80+	210°	50,000	5	✓
09735	LED14WT8/P/48/840-G8D	4'	1,800	14W	120~277V	4000K	80+	210°	50,000	5	✓
09734	LED14WT8/P/48/850-G8D	4'	1,800	14W	120~277V	5000K	80+	210°	50,000	5	✓
09362	LED17WT8/P/48/835-G7D	4'	2,100	17W	120~277V	3500K	80+	210°	50,000	5	✓
09733	LED17WT8/P/48/835-G8D	4'	2,100	17W	120~277V	3500K	80+	210°	50,000	5	✓
09732	LED17WT8/P/48/840-G8D	4'	2,200	17W	120~277V	4000K	80+	210°	50,000	5	✓
09731	LED17WT8/P/48/850-G8D	4'	2,200	17W	120~277V	5000K	80+	210°	50,000	5	✓



LitespanLED® T8 Linear Bypass/Line Voltage

Order Code	Item	Length	Lm	W	V	CCT	CRI	Bm	Life/Hrs L70	Photo #	DLC
09322	LED9WT8F/24/835K-G7D	2'	1,100	9W	120~277V	3500K	80+	220°	50,000	1	✓
09323	LED9WT8F/24/840K-G7D	2'	1,150	9W	120~277V	4000K	80+	220°	50,000	1	✓
09324	LED9WT8F/24/850K-G7D	2'	1,150	9W	120~277V	5000K	80+	220°	50,000	1	✓
09666	LED11.5WT8/48/835-G7D	4'	1,700	12W	120~277V	3500K	80+	220°	50,000	1	✓
09669	LED11.5WT8/48/835-PET-G7D	4'	1,700	12W	120~277V	3500K	80+	220°	50,000	1	✓
09667	LED11.5WT8/48/840-G7D	4'	1,800	12W	120~277V	4000K	80+	220°	50,000	1	✓
09670	LED11.5WT8/48/840-PET-G7D	4'	1,800	12W	120~277V	4000K	80+	220°	50,000	1	✓
09668	LED11.5WT8/48/850-G7D	4'	1,800	12W	120~277V	5000K	80+	220°	50,000	1	✓
09671	LED11.5WT8/48/850-PET-G7D	4'	1,800	12W	120~277V	5000K	80+	220°	50,000	1	✓
09371	LED12WT8/PRM/48/835-G7D	4'	1,700	12W	120~277V	3500K	80+	210°	50,000	1	✓
09319	LED12WT8F/36/835K-G7D	3'	1,400	12W	120~277V	3500K	80+	220°	50,000	1	
09320	LED12WT8F/36/840K-G7D	3'	1,450	12W	120~277V	4000K	80+	220°	50,000	1	
09321	LED12WT8F/36/850K-G7D	3'	1,450	12W	120~277V	5000K	80+	220°	50,000	1	
09288	LED15WT8F/48/835K-G7D	4'	1,700	15W	120~277V	3500K	80+	220°	50,000	1	✓
09278	LED15WT8F/48/840K-G7D	4'	1,800	15W	120~277V	4000K	80+	220°	50,000	1	✓
09279	LED15WT8F/48/850K-G7D	4'	1,800	15W	120~277V	5000K	80+	220°	50,000	1	✓
09396	LED18WT8F/48/835-G7D	4'	2,100	18W	120~277V	3500K	80+	210°	50,000	1	✓
09893	LED18WT8F/48/835-G7D-347V*	4'	2,100	18W	347V	3500K	80+	210°	50,000	1	✓
09397	LED18WT8F/48/840-G7D	4'	2,200	18W	120~277V	4000K	80+	210°	50,000	1	✓
09891	LED18WT8F/48/840-G7D-347V*	4'	2,200	18W	347V	4000K	80+	210°	50,000	1	✓
09398	LED18WT8F/48/850-G7D	4'	2,200	18W	120~277V	5000K	80+	210°	50,000	1	✓
09894	LED18WT8F/48/850-G7D-347V*	4'	2,200	18W	347V	5000K	80+	210°	50,000	1	✓

*Canada only.

LitespanLED® 8' Linear Bypass/Line Voltage

Order Code	Item	Length	Lm	W	V	CCT	CRI	Bm	Life/Hrs L70	Photo #	DLC
09567	LED43WT8/96/840-DBL-G7D	8'	5,500	43W	120~277V	4000K	80+		50,000	6	
09568	LED43WT8/96/850-DBL-G7D	8'	5,500	43W	120~277V	5000K	80+		50,000	6	

LitespanLED® T8 Double-Ended Line Voltage

Order Code	Item	Length	Lm	W	V	CCT	CRI	Bm	Life/Hrs L70	Photo #	DLC
09598	LED9WT8/24/840-DBL-G7D	2'	1,150	9W	120~277V	4000K	80+	210°	50,000	7	✓
09599	LED9WT8/24/850-DBL-G7D	2'	1,150	9W	120~277V	5000K	80+	210°	50,000	7	✓
09600	LED12WT8/36/835-DBL-G7D	3'	1,400	12W	120~277V	3500K	80+	210°	50,000	7	
09601	LED12WT8/36/840-DBL-G7D	3'	1,450	12W	120~277V	4000K	80+	210°	50,000	7	
09602	LED12WT8/36/850-DBL-G7D	3'	1,450	12W	120~277V	5000K	80+	210°	50,000	7	
09594	LED14WT8/48/835-DBL-G7D	4'	1,700	14W	120~277V	3500K	80+	210°	50,000	7	✓
09595	LED14WT8/48/840-DBL-G7D	4'	1,800	14W	120~277V	4000K	80+	210°	50,000	7	✓
09603	LED14WT8/48/850-DBL-G7D	4'	1,800	14W	120~277V	5000K	80+	210°	50,000	7	✓
09604	LED17WT8/48/835-DBL-G7D	4'	2,100	17W	120~277V	3500K	80+	210°	50,000	7	✓
09605	LED17WT8/48/840-DBL-G7D	4'	2,200	17W	120~277V	4000K	80+	210°	50,000	7	✓
09606	LED17WT8/48/850-DBL-G7D	4'	2,200	17W	120~277V	5000K	80+	210°	50,000	7	✓



LitespanLED® T5 Direct Fit Replacement Lamps

Order Code	Item	Length	Lm	Nominal Lamp W	V (Ballast Dependent)	CCT	CRI	Bm	Life/Hrs L70	Photo #	DLC
09553	LED11WT5HO/22/835-G7DR	2'	1,350	11W	120~277V	3500K	80+	185°	50,000	8	
09554	LED11WT5HO/22/840-G7DR	2'	1,400	11W	120~277V	4000K	80+	185°	50,000	8	
09555	LED11WT5HO/22/850-G7DR	2'	1,400	11W	120~277V	5000K	80+	185°	50,000	8	
09556	LED12.5WT5HE/46/835-G7DR	4'	1,700	13W	120~277V	3500K	80+	185°	50,000	8	
09557	LED12.5WT5HE/46/840-G7DR	4'	1,800	13W	120~277V	4000K	80+	185°	50,000	8	
09558	LED12.5WT5HE/46/850-G7DR	4'	1,800	13W	120~277V	5000K	80+	185°	50,000	8	
09549	LED25WT5HO/46/835-G7DR	4'	3,200	25W	120~277V	3500K	80+	185°	50,000	8	✓
09550	LED25WT5HO/46/840-G7DR	4'	3,500	25W	120~277V	4000K	80+	185°	50,000	8	✓
09551	LED25WT5HO/46/850-G7DR	4'	3,500	25W	120~277V	5000K	80+	185°	50,000	8	✓
09928	LED25WT5HO/46/835-G8DR	4'	3,500	25W	120~277V	3500K	80+	185°	50,000	8	✓
09930	LED25WT5HO/46/840-G8DR	4'	3,500	25W	120~277V	4000K	80+	185°	50,000	8	✓
09900	LED25WT5HO/46/850-G8DR	4'	3,500	25W	120~277V	5000K	80+	185°	50,000	8	✓

LitespanLED® T5 Double-Ended Line Voltage

Order Code	Item	Length	Lm	W	V	CCT	CRI	Bm	Life/Hrs L70	Photo #	DLC
09949	LED25WT5HO/46/835-G8D	4'	3,300	25W	120~277V	3500K	80+	185°	50,000	8	✓
09947	LED25WT5HO/46/840-G8D	4'	3,500	25W	120~277V	4000K	80+	185°	50,000	8	✓
09948	LED25WT5HO/46/850-G8D	4'	3,500	25W	120~277V	5000K	80+	185°	50,000	8	✓





A19/A21 Replacement Lamps

- Direct replacement for incandescent A lamps
- 300° omni beam angle is ideal for table lamps, wall sconces, and luminous globe fixtures
- 80% more efficient and 30x longer life than incandescent
- Compatible with a wide array of dimmers
- Instant-on with no warm up, unlike CFLs
- Available in 2700K, 3000K, and 4000K CCT
- Shatter-resistant for reduced risk of injury and breakage

LitespanLED® A Lamps

Order Code	Item	Lm	W	CCT	CRI	V	Life/Hrs L70	Base	Replaces Incan.	Photo #	ES
09976	LED5WA15/OMN/BLUE-G8	-	5W	Blue	-	120V	10,000	E26	-	1	
09981	LED5WA15/OMN/RED-G8	-	5W	Red	-	120V	10,000	E26	-	1	
09973	LED5WA15/OMN/YELLOW-G8	-	5W	Yellow	-	120V	10,000	E26	-	1	
10057	LED8WA15/OMN/827-DIM-G8	800	8W	2700K	80+	120V	15,000	E26	60W	1	★
10058	LED8WA15/OMN/830-DIM-G8	800	8W	3000K	80+	120V	15,000	E26	60W	1	★
10059	LED8WA15/OMN/840-DIM-G8	800	8W	4000K	80+	120V	15,000	E26	60W	1	★
09841	LED8WA15/OMN/830K-DIM-G7 2PK*	800	8W	3000K	80+	120V	15,000	E26	60W	1	★
09842	LED8WA15/OMN/840K-DIM-G7 2PK*	800	8W	4000K	80+	120V	15,000	E26	60W	1	★
09132	LED6WA19/300/827K-DIM-G6	470	6W	2700K	80+	120V	25,000	E26	40W	2	
09882	LED6WA19/OMN/827-DIM-G8	480	6W	2700K	80+	120V	25,000	E26	40W	2	★
09748	LED6WA19/OMN/830-DIM-G8	480	6W	3000K	80+	120V	25,000	E26	40W	2	★
09750	LED6WA19/OMN/830-G8	480	6W	3000K	80+	120V	25,000	E26	40W	2	★
09749	LED6WA19/OMN/840-DIM-G8	480	6W	4000K	80+	120V	25,000	E26	40W	2	★
09751	LED6WA19/OMN/840-G8	480	6W	4000K	80+	120V	25,000	E26	40W	2	★
60421	LED6WA19/OMN/827K-DIM-G7 2PK	480	6W	2700K	80+	120V	15,000	E26	40W	2	★
60422	LED6WA19/OMN/830K-DIM-G7 2PK	480	6W	3000K	80+	120V	15,000	E26	40W	2	★
60423	LED6WA19/OMN/840K-DIM-G7 2PK	480	6W	4000K	80+	120V	15,000	E26	40W	2	★
08925	LED9WA19/300/840K-GU24-DIM-G5	800	9W	4000K	80+	120V	25,000	GU24	60W	3	
09895	LED9WA19/OMN/827-DIM-G8	800	9W	2700K	80+	120V	25,000	E26	60W	2	★
09442	LED9WA19/OMN/827GU24DIMG7 2PK	800	9W	2700K	80+	120V	25,000	GU24	60W	3	★
60427	LED9WA19/OMN/827K-DEC-G7 2PK	800	9W	2700K	80+	120V	25,000	E26	60W	2	★
09896	LED9WA19/OMN/830-DIM-G8	800	9W	3000K	80+	120V	25,000	E26	60W	2	★
09443	LED9WA19/OMN/830GU24DIMG7 2PK	800	9W	3000K	80+	120V	25,000	GU24	60W	3	★

Continued on next page >>>

*Canada only.



5 YEAR WARRANTY



LitespanLED® A Lamps

Order Code	Item	Lm	W	CCT	CRI	V	Life/Hrs L70	Base	Replaces Incan.	Photo #	ES
09752	LED9WA19/OMN/840-DIM-G8	800	9W	4000K	80+	120V	25,000	E26	60W	2	★
10060	LED9WA19/OMN/850-DIM-G8	800	9W	5000K	80+	120V	25,000	E26	60W	2	★
09974	LED9WA19/OMN/827-GU24-DIM-G8	800	9W	2700K	80+	120V	25,000	GU24	60W	3	★
09975	LED9WA19/OMN/830-GU24-DIM-G8	800	9W	3000K	80+	120V	25,000	GU24	60W	3	★
09444	LED9WA19/OMN/840GU24DIMG7 2PK	800	9W	4000K	80+	120V	25,000	GU24	60W	3	★
60429	LED9WA19/OMN/840K-DEC-G7 2PK	800	9W	4000K	80+	120V	25,000	E26	60W	2	★
60426	LED9WA19/OMN/840K-DIM-G7 2PK	800	9W	4000K	80+	120V	15,000	E26	60W	2	★
09753	LED9.5WA19/OMN/830-G8	800	9.5W	3000K	80+	120V		E26	60W	2	★
09941	LED9.5WA19/OMN/840-G8	800	9.5W	4000K	80+	120V		E26	60W	2	★
08914	LED11WA19/300/827K-DIM-G5	1,100	11W	2700K	80+	120V	25,000	E26	75W	2	
08927	LED11WA19/300/830K-GU24-DIM-G5	1,100	11W	3000K	80+	120V	25,000	GU24	75W	3	
09885	LED11WA19/OMN/827-DIM-G8	1,100	11W	2700K	80+	120V	25,000	E26	75W	2	★
09445	LED11WA19/OMN/827GU24DIMG7 2PK	1,100	11W	2700K	80+	120V	25,000	GU24	75W	3	★
60430	LED11WA19/OMN/827K-DIM-G7 2PK	1,100	11W	2700K	80+	120V	15,000	E26	75W	2	★
09446	LED11WA19/OMN/830GU24DIMG7 2PK	1,100	11W	3000K	80+	120V	25,000	GU24	75W	3	★
60431	LED11WA19/OMN/830K-DIM-G7 2PK	1,100	11W	3000K	80+	120V	15,000	E26	75W	2	★
09447	LED11WA19/OMN/840GU24DIMG7 2PK	1,100	11W	4000K	80+	120V	25,000	GU24	75W	3	★
60432	LED11WA19/OMN/840K-DIM-G7 2PK	1,100	11W	4000K	80+	120V	15,000	E26	75W	2	★
09942	LED11WA19/OMN/830-DIM-G8	1,100	11W	3000K	80+	120V	15,000	E26	75W	2	★
10014	LED11WA19/OMN/830-GU24-DIM-G8	1,100	11W	3000K	80+	120V	15,000	GU24	75W	3	★
09943	LED11WA19/OMN/840-DIM-G8	1,100	11W	4000K	80+	120V	15,000	E26	75W	2	★
10061	LED11WA19/OMN/850-DIM-G8	1,100	11W	5000K	80+	120V	15,000	E26	75W	2	★
09886	LED15WA19/OMN/827-DIM-G8	1,600	15W	2700K	80+	120V	15,000	E26	100W	2	★
09944	LED15WA19/OMN/830-DIM-G8	1,600	15W	3000K	80+	120V	15,000	E26	100W	2	★
09945	LED15WA19/OMN/840-DIM-G8	1,600	15W	4000K	80+	120V	15,000	E26	100W	2	★
09946	LED15WA19/OMN/850-DIM-G8	1,600	15W	5000K	80+	120V	15,000	E26	100W	2	★
08929	LED15WA21/300/827K-GU24-DIM-G5	1,600	15W	2700K	80+	120V	25,000	GU24	100W	5	
08930	LED15WA21/300/830K-GU24-DIM-G5	1,600	15W	3000K	80+	120V	25,000	GU24	100W	5	
08931	LED15WA21/300/840K-GU24-DIM-G5	1,600	15W	4000K	80+	120V	25,000	GU24	100W	5	
60433	LED15WA21/OMN/827K-DIM-G7 2PK	1,600	15W	2700K	80+	120V	15,000	E26	100W	4	★
60434	LED15WA21/OMN/830K-DIM-G7 2PK	1,600	15W	3000K	80+	120V	15,000	E26	100W	4	★
60435	LED15WA21/OMN/840K-DIM-G7 2PK	1,600	15W	4000K	80+	120V	15,000	E26	100W	4	★
60436	LED15WA21/OMN/850K-DIM-G7 2PK	1,600	15W	5000K	80+	120V	15,000	E26	100W	4	★
60409	LED16WA21/ADV/827K-DIM-G7 2PK	1,550	16W	2700K	80+	120V	10,000	E26	100W	4	

Advantage™ A19 Lamps

Order Code	Item	Lm	W	CCT	CRI	V	Life/Hrs L70	Base	Replaces Incan.	Photo #	ES
09144	LED6WA19/240/830K-DIM-G6A	440	6W	3000K	80+	120V	15,000	E26	40W	2	
09141	LED6WA19/240/830K-G6A	440	6W	3000K	80+	120V	15,000	E26	40W	2	
09145	LED6WA19/240/840K-DIM-G6A	440	6W	4000K	80+	120V	15,000	E26	40W	2	
09142	LED6WA19/240/840K-G6A	440	6W	4000K	80+	120V	15,000	E26	40W	2	
09499	LED6WA19/ADV/827-DIM-G7A 2PK	450	6W	2700K	80+	120V	15,000	E26	40W	2	
09503	LED6WA19/ADV/827-G7A 2PK	450	6W	2700K	80+	120V	15,000	E26	40W	2	
09504	LED6WA19/ADV/830-G7A 2PK	450	6W	3000K	80+	120V	15,000	E26	40W	2	
09505	LED6WA19/ADV/840-G7A 2PK	450	6W	4000K	80+	120V	15,000	E26	40W	2	

Continued on next page >>>



Advantage™ A19 Lamps

Order Code	Item	Lm	W	CCT	CRI	V	Life/Hrs L70	Base	Replaces Incan.	Photo #	ES
09461	LED6WA19/ADV/850-DIM-G7 2PK	440	6W	5000K	80+	120V	15,000	E26	40W	2	
90029	LED7WA19/240/850K-DIM-G4A	420	7W	5000K	80+	120V	25,000	E26	60W	2	
09987	LED9WA19/ADV/830-DIM-G8	750	9W	3000K	80+	120V	15,000	E26	60W	2	
09294	LED9WA19/240/830K-G6A 2PK	760	9W	3000K	80+	120V	15,000	E26	60W	2	
09506	LED9WA19/ADV/827-DIM-G7A 2PK	750	9W	2700K	80+	120V	15,000	E26	60W	2	
09510	LED9WA19/ADV/827-G7A 2PK	750	9W	2700K	80+	120V	15,000	E26	60W	2	
09517	LED9WA19/ADV/830-DIM-G7A 2PK	750	9W	3000K	80+	120V	15,000	E26	60W	2	
09511	LED9WA19/ADV/830-G7A 2PK	750	9W	3000K	80+	120V	15,000	E26	60W	2	
09508	LED9WA19/ADV/840-DIM-G7A 2PK	750	9W	4000K	80+	120V	15,000	E26	60W	2	
09512	LED9WA19/ADV/840-G7A 2PK	750	9W	4000K	80+	120V	15,000	E26	60W	2	
09509	LED9WA19/ADV/850-DIM-G7A 2PK	750	9W	5000K	80+	120V	15,000	E26	60W	2	
60405	LED12WA19/ADV/827K-DIM-G7 2PK	1,050	12W	2700K	80+	120V	10,000	E26	75W	2	
60413	LED12WA19/ADV/827K-G7 2PK	1,050	12W	2700K	80+	120V	10,000	E26	75W	2	
60406	LED12WA19/ADV/830K-DIM-G7 2PK	1,050	12W	3000K	80+	120V	10,000	E26	75W	2	
60414	LED12WA19/ADV/830K-G7 2PK	1,050	12W	3000K	80+	120V	10,000	E26	75W	2	
60407	LED12WA19/ADV/840K-DIM-G7 2PK	1,050	12W	4000K	80+	120V	10,000	E26	75W	2	
60415	LED12WA19/ADV/840K-G7 2PK	1,050	12W	4000K	80+	120V	10,000	E26	75W	2	
60408	LED12WA19/ADV/850K-DIM-G7 2PK	1,050	12W	5000K	80+	120V	10,000	E26	75W	2	
60416	LED12WA19/ADV/850K-G7 2PK	1,050	12W	5000K	80+	120V	10,000	E26	75W	2	
60409	LED16WA21/ADV/827K-DIM-G7 2PK	1,550	16W	2700K	80+	120V	10,000	E26	100W	3	
60417	LED16WA21/ADV/827K-G7 2PK	1,550	16W	2700K	80+	120V	10,000	E26	100W	3	
60410	LED16WA21/ADV/830K-DIM-G7 2PK	1,550	16W	3000K	80+	120V	10,000	E26	100W	3	
60418	LED16WA21/ADV/830K-G7 2PK	1,550	16W	3000K	80+	120V	10,000	E26	100W	3	
60411	LED16WA21/ADV/840K-DIM-G7 2PK	1,550	16W	4000K	80+	120V	10,000	E26	100W	3	
60419	LED16WA21/ADV/840K-G7 2PK	1,550	16W	4000K	80+	120V	10,000	E26	100W	3	
60412	LED16WA21/ADV/850K-DIM-G7 2PK	1,550	16W	5000K	80+	120V	10,000	E26	100W	3	
60420	LED16WA21/ADV/850K-G7 2PK	1,550	16W	5000K	80+	120V	10,000	E26	100W	3	



Filament Dimmable Decorative Lamps

- LED lamp with the same vintage look and feel as traditional incandescent filament lamps
- 80% more efficient and 20x longer life than incandescent
- 320° omni-directional light source adds warm ambient glow to room décor
- 2200K amber and 2700K clear available in decorative shapes
- Compatible with a wide array of leading edge TRIAC dimmers
- Suitable for use in damp locations
- Suitable for use in totally enclosed fixtures
- Contains no lead or mercury; RoHS compliant
- 3 year limited warranty

Advantage™ LED Filament Decorative Lamps

Order Code	Item	Lm	W	CCT	CRI	V	Life/Hrs L70	Base	Replaces Incan.	Photo #	ES
09865	LED2WT6E12/FIL/827-DIM-G7	120	2W	2700K	80+	120V	15,000	E12	15W	1	
09858	LED2.5WB11E12/FIL/827-DIM-G7	200	3W	2700K	80+	120V	15,000	E12	25W	2	★
09869	LED2.5WT10/FIL/827-DIM-G7	250	3W	2700K	80+	120V	15,000	E26	25W	3	
09866	LED2.5WT6.5E17/FIL/827-DIM-G7	200	3W	2700K	80+	120V	15,000	E17	20W	4	
09311	LED5WB11E26/FIL/827K-DIM-G6	450	4W	2700K	80+	120V	15,000	E26	40W	5	
09855	LED4WA15/FIL/827-DIM-G7	300	4W	2700K	80+	120V	15,000	E26	25W	6	
09863	LED4WS14/FIL/822-DIM-G7	250	4W	2700K	80+	120V	15,000	E26	25W	7	
09864	LED4WS14/FIL/827-DIM-G7	300	4W	2700K	80+	120V	15,000	E26	40W	7	
09860	LED4WBA11E12/FIL/827-DIM-G7	300	4W	2700K	80+	120V	15,000	E12	40W	8	
09892	LED4WB11E12/FIL/827-DIM-G7	300	4W	2700K	80+	120V	15,000	E12	40W	2	★
09861	LED4WG16/FIL/827-DIM-G7	350	4W	2700K	80+	120V	15,000	E26	40W	9	
09879	LED4WST19/FIL/822-DIM-G7	400	4W	2700K	80+	120V	15,000	E26	40W	10	
09870	LED4WT10/FIL/827-DIM-G7	450	4W	2700K	80+	120V	15,000	E26	40W	3	
09867	LED4WT6.5E17/FIL/827-DIM-G7	350	4W	2700K	80+	120V	15,000	E17	25W	4	
09856	LED4.5WA15/FIL/827-DIM-G7	450	5W	2700K	80+	120V	15,000	E26	40W	6	

Continued on next page >>>



Advantage™ LED Filament Decorative Lamps

Order Code	Item	Lm	W	CCT	CRI	V	Life/Hrs L70	Base	Replaces Incan.	Photo #	ES
09871	LED4.5WA19/FIL/822-DIM-G7	350	5W	2200K	80+	120V	15,000	E26	25W	11	
09857	LED4.5WA19/FIL/SB/827-DIM-G7	400	5W	2700K	80+	120V	15,000	E26	25W	12	
09859	LED4.5WB11E12/FIL/827-DIM-G7	500	5W	2700K	80+	120V	15,000	E12	60W	2	
09862	LED4.5WG16/FIL/827-DIM-G7	500	5W	2700K	80+	120V	15,000	E26	60W	9	
09875	LED4.5WG25/FIL/827-DIM-G7	470	5W	2700K	80+	120V	15,000	E26	40W	13	
09868	LED4.5WT6.5E17/FIL/827-DIM-G7	450	5W	2700K	80+	120V	15,000	E17	40W	4	
09878	LED5WB11E26/FIL/827-DIM-G7	500	5W	2700K	80+	120V	15,000	E26	60W	14	
09314	LED5WG40/FIL/822K-DIM-G6	400	5W	2200K	80+	120V	15,000	E26	60W	15	
09315	LED5WST19/FIL/822K-DIM-G6	400	5W	2200K	80+	120V	15,000	E26	40W	16	
09313	LED6WG25/FIL/827K-DIM-G6	400	6W	2700K	80+	120V	15,000	E26	40W	17	
09441	LED7WA19/FIL/SB/827K-DIM-G7	700	7W	2700K	80+	120V	15,000	E26	60W	12	
09877	LED7WA19/FIL/827-DIM-G7	800	7W	2700K	80+	120V	15,000	E26	60W	11	★



3 YEAR WARRANTY





PL CFL Replacement Lamps

- Directly replaces PL compact fluorescent lamps
- Direct fit plug-and-play solution
- Available in horizontal or vertical orientation
- Choice of 2700K, 3000K, 3500K and 4000K CCT
- Instant-on with no warmup, unlike compact fluorescent
- Shatter-resistant for reduced risk of injury and breakage
- Dimmable models available (ballast dependent)
- Environmentally friendly; contains no glass, lead or mercury

LitespanLED® PL Replacement Lamps

Order Code	Item	Lm	W	CCT	CRI	V	Life/Hrs L70	Base	Replaces CFL	Photo #	DLC
09526	LED5W2PH/G23/827-G7	475	5W	2700K	80+	120~277V	50,000	G23	5/7/9W	1	
09528	LED5W2PH/G23/840-G7	500	5W	4000K	80+	120~277V	50,000	G23	5/7/9W	1	
09530	LED7W2PH/GX23/827-G7	650	7W	2700K	80+	120~277V	50,000	GX23	13W	2	
09531	LED7W2PH/GX23/835-G7	650	7W	3500K	80+	120~277V	50,000	GX23	13W	2	
09532	LED7W2PH/GX23/840-G7	700	7W	4000K	80+	120~277V	50,000	GX23	13W	2	
09533	LED7W2PH/GX23/850-G7	700	7W	5000K	80+	120~277V	50,000	GX23	13W	2	
09332	LED9W2PH/827DR-G6	850	9W	2700K	80+	120~277V	50,000	G24d	26W	3	
09250	LED9W2PH/830DR-G6	850	9W	3000K	80+	120~277V	50,000	G24d	26W	3	
09251	LED9W2PH/835DR-G6	850	9W	3500K	80+	120~277V	50,000	G24d	26W	3	
09252	LED9W2PH/840DR-G6	900	9W	4000K	80+	120~277V	50,000	G24d	26W	3	
09334	LED9W2PV/827DR-G6	850	9W	2700K	80+	120~277V	50,000	G24d	26W	4	
09253	LED9W2PV/830DR-G6	850	9W	3000K	80+	120~277V	50,000	G24d	26W	4	
09254	LED9W2PV/835DR-G6	850	9W	3500K	80+	120~277V	50,000	G24d	26W	4	
09255	LED9W2PV/840DR-G6	900	9W	4000K	80+	120~277V	50,000	G24d	26W	4	
09938	LED9W4PH/827DR-G7	900	9W	2700K	80+	120~277V	50,000	G24q	18W	5	
09901	LED9W4PH/830DR-G7	950	9W	3000K	80+	120~277V	50,000	G24q	18W	5	
09902	LED9W4PH/835DR-G7	950	9W	3500K	80+	120~277V	50,000	G24q	18W	5	
09903	LED9W4PH/840DR-G7	1,000	9W	4000K	80+	120~277V	50,000	G24q	18W	5	
09331	LED9W4PH/827DR-G6	850	9W	2700K	80+	120~277V	50,000	G24q	26/32/42W	6	
09244	LED9W4PH/830DR-G6	850	9W	3000K	80+	120~277V	50,000	G24q	26/32/42W	6	✓
09246	LED9W4PH/840DR-G6	900	9W	4000K	80+	120~277V	50,000	G24q	26/32/42W	6	✓

Continued on next page >>>



LitespanLED® PL Replacement Lamps


Order Code	Item	Lm	W	CCT	CRI	V	Life/Hrs L70	Base	Replaces CFL	Photo #	DLC
09939	LED9W4PV/827DR-G7	900	9W	2700K	80+	120~277V	50,000	G24q	18W	7	
09940	LED9W4PV/830DR-G7	950	9W	3000K	80+	120~277V	50,000	G24q	18W	7	
09925	LED9W4PV/835DR-G7	950	9W	3500K	80+	120~277V	50,000	G24q	18W	7	
09926	LED9W4PV/840DR-G7	1,000	9W	4000K	80+	120~277V	50,000	G24q	18W	7	
09333	LED9W4PV/827DR-G6	850	9W	2700K	80+	120~277V	50,000	G24q	26/32/42W	8	
09247	LED9W4PV/830DR-G6	850	9W	3000K	80+	120~277V	50,000	G24q	26/32/42W	8	✓
09249	LED9W4PV/840DR-G6	900	9W	4000K	80+	120~277V	50,000	G24q	26/32/42W	8	✓



5 YEAR WARRANTY

UL US

CLASSIFIED UL US



PLL Replacement Lamps

- Solid state replacement for 2' 40W PLL compact fluorescent lamps with 2G11 base
- Frosted lens for uniform diffuse appearance
- Ultra-high performance LEDs deliver 100 lpw
- Lifetime exceeds 50,000 hrs
- Up to 50% instant energy savings
- Choice of 3000K, 3500K, 4000K, and 5000K CCT
- Instant-on with no warm up, unlike fluorescents

LitespanLED® PLL Replacement Lamps

Order Code	Item	Lm	W	CCT	CRI	V	Life/Hrs L70	Base	Bm	Photo #	ES
60461	LED23W/PLL/830-G7DR	2,600	23W	3000K	82+	120~277V	50,000	2G11	120°	1	
60462	LED23W/PLL/835-G7DR	2,600	23W	3500K	82+	120~277V	50,000	2G11	120°	1	
60463	LED23W/PLL/840-G7DR	2,800	23W	4000K	82+	120~277V	50,000	2G11	120°	1	
60464	LED23W/PLL/850-G7DR	2,800	23W	5000K	82+	120~277V	50,000	2G11	120°	1	



5 YEAR WARRANTY

c UL US LISTED



BR Replacement Lamps

- Direct replacement for incandescent BR lamps
- 80% more efficient and 20x longer life than incandescent
- Smooth aluminum body with ANSI standard form factor
- Acceptable for ICAT rated downlights

LitespanLED® BR Lamps

Order Code	Item	Lm	W	CCT	CRI	V	Life/Hrs L70	Base	Replaces Incan.	Photo #	ES
10005	LED7WBR20/830-DIM-G8	550	7W	3000K	80+	120V	25,000	E26	55W	1	
10006	LED7WBR20/840-DIM-G8	550	7W	4000K	80+	120V	25,000	E26	55W	1	
08932	LED7WBR20/827K-DIM-G5	550	7W	2700K	80+	120V	25,000	E26	55W	1	★
09792	LED7WBR20/830-DIM-G5	550	7W	3000K	80+	120V	25,000	E26	55W	1	
09999	LED8WBR30/827K-DIM-G8	650	8W	2700K	80+	120V	25,000	E26	65W	2	
10000	LED8WBR30/830-DIM-G8	650	8W	3000K	80+	120V	25,000	E26	65W	2	
10001	LED8WBR30/840-DIM-G8	650	8W	4000K	80+	120V	25,000	E26	65W	2	
08998	LED8WBR30/827K-DIM-G5	650	8W	2700K	80+	120V	25,000	E26	65W	2	★
08999	LED8WBR30/830K-DIM-G5	650	8W	3000K	80+	120V	25,000	E26	65W	2	★
09000	LED8WBR30/840K-DIM-G5	650	8W	4000K	80+	120V	25,000	E26	65W	2	★
10002	LED11WBR30/827-DIM-G8	850	11W	2700K	80+	120V	25,000	E26	65W	2	
10003	LED11WBR30/830-DIM-G8	850	11W	3000K	80+	120V	25,000	E26	65W	2	
10004	LED11WBR30/840-DIM-G8	850	11W	4000K	80+	120V	25,000	E26	65W	2	
08937	LED11WBR30/830K-DIM-G5	850	11W	3000K	80+	120V	25,000	E26	65W	2	★
08938	LED11WBR30/840K-DIM-G5	850	11W	4000K	80+	120V	25,000	E26	65W	2	★
08936	LED11WBR30/827K-DIM-G5	850	11W	2700K	80+	120V	25,000	E26	65W	2	★
09111	LED11WBR30/850K-DIM-G5	850	11W	5000K	80+	120V	25,000	E26	65W	2	★
09351	LED11WBR30/927K-DIM-G6	800	11W	2700K	80+	120V	25,000	E26	65W	2	★
09352	LED11WBR30/930K-DIM-G6	800	11W	3000K	80+	120V	25,000	E26	65W	2	★
09998	LED12WBR40/830-DIM-G8	1,050	12W	3000K	80+	120V	25,000	E26	80W	3	
08939	LED12WBR40/827K-DIM-G5	1,050	12W	2700K	80+	120V	25,000	E26	80W	3	★
08940	LED12WBR40/830K-DIM-G5	1,050	12W	3000K	80+	120V	25,000	E26	80W	3	★
08941	LED12WBR40/840K-DIM-G5	1,050	12W	4000K	80+	120V	25,000	E26	80W	3	★
09353	LED13WBR40/927K-DIM-G5	1,000	13W	2700K	80+	120V	25,000	E26	80W	3	★
09354	LED13WBR40/930K-DIM-G5	1,000	13W	3000K	80+	120V	25,000	E26	80W	3	★
09996	LED17WBR40/830-DIM-G8	1,400	17W	3000K	80+	120V	25,000	E26	100W	3	
09997	LED17WBR40/840-DIM-G8	1,400	17W	4000K	80+	120V	25,000	E26	100W	3	
08942	LED17WBR40/827K-DIM-G5	1,400	17W	2700K	80+	120V	25,000	E26	100W	3	★
08943	LED17WBR40/830K-DIM-G5	1,400	17W	3000K	80+	120V	25,000	E26	100W	3	★
08944	LED17WBR40/840K-DIM-G5	1,400	17W	4000K	80+	120V	25,000	E26	100W	3	★



5 YEAR WARRANTY





PAR Replacement Lamps

- Direct replacement for halogen PARs
- Compatible with a wide array of dimmers
- 25,000 hour rated life for ENERGY STAR® Approved lamps
- 50,000 hour design life
- Up to 80% electricity savings vs. halogen
- Choice of 2700K, 3000K and 4000K CCT
- Environmentally friendly: contains no glass, mercury, or lead

LitespanLED® PAR Lamps

Order Code	Item	Lm	W	CCT	CRI	V	Life/Hrs L70	Base	Replaces Incan.	Photo #	ES
09041	LED7WPAR16/FL/827K-DIM-G5	490	7W	2700K	80+	120V	25,000	E26	50W	1	★
09042	LED7WPAR16/FL/830K-DIM-G5	490	7W	3000K	80+	120V	25,000	E26	50W	1	★
09043	LED7WPAR16/FL/840K-DIM-G5	490	7W	4000K	80+	120V	25,000	E26	50W	1	★
09038	LED7WPAR16/NFL/827K-DIM-G5	490	7W	2700K	80+	120V	25,000	E26	50W	1	★
09039	LED7WPAR16/NFL/830K-DIM-G5	490	7W	3000K	80+	120V	25,000	E26	50W	1	★
09040	LED7WPAR16/NFL/840K-DIM-G5	490	7W	4000K	80+	120V	25,000	E26	50W	1	★
09970	LED7WPAR20/FL/827-DIM-G8	500	7W	2700K	80+	120V	25,000	E26	50W	2	
09971	LED7WPAR20/FL/830-DIM-G8	500	7W	3000K	80+	120V	25,000	E26	50W	2	
09984	LED7WPAR20/FL/840-DIM-G8	500	7W	4000K	80+	120V	25,000	E26	50W	2	
09985	LED7WPAR20/NFL/827-DIM-G8	500	7W	2700K	80+	120V	25,000	E26	50W	2	
09986	LED7WPAR20/NFL/830-DIM-G8	500	7W	3000K	80+	120V	25,000	E26	50W	2	
09972	LED7WPAR20/NFL/840-DIM-G8	500	7W	4000K	80+	120V	25,000	E26	50W	2	
09184	LED7WPAR20/FL/827K-DIM-G6	470	7W	2700K	80+	120V	25,000	E26	50W	2	★
09186	LED7WPAR20/FL/840K-DIM-G6	470	7W	4000K	80+	120V	25,000	E26	50W	2	★
09187	LED7WPAR20/NFL/827K-DIM-G6	470	7W	2700K	80+	120V	25,000	E26	50W	2	★
09188	LED7WPAR20/NFL/830K-DIM-G6	470	7W	3000K	80+	120V	25,000	E26	50W	2	★
90019	LED7WPAR20/NFL/840K-DIM-G4A	500	7W	4000K	80+	120V	25,000	E26	55W	2	
09189	LED7WPAR20/NFL/840K-DIM-G6	470	7W	4000K	80+	120V	25,000	E26	50W	2	★
09993	LED11WPAR30/FL/827-DIM-G8	850	11W	2700K	80+	120V	25,000	E26	75W	3	
09994	LED11WPAR30/FL/850-DIM-G8	850	11W	5000K	80+	120V	25,000	E26	75W	3	
09155	LED11WPAR30/FL/827K-DIM-G6	850	11W	2700K	80+	120V	25,000	E26	75W	3	★
09156	LED11WPAR30/FL/830K-DIM-G6	850	11W	3000K	80+	120V	25,000	E26	75W	3	★
09157	LED11WPAR30/FL/840K-DIM-G6	850	11W	4000K	80+	120V	25,000	E26	75W	3	★
09325	LED11WPAR30/FL/850K-DIM-G6	850	11W	5000K	80+	120V	25,000	E26	75W	3	★

Continued on next page >>>



5 YEAR WARRANTY



LitespanLED® PAR Lamps

Order Code	Item	Lm	W	CCT	CRI	V	Life/Hrs L70	Base	Replaces Incan.	Photo #	ES
09158	LED11WPAR30/NFL/827K-DIM-G6	850	11W	2700K	80+	120V	25,000	E26	75W	3	★
09159	LED11WPAR30/NFL/830K-DIM-G6	850	11W	3000K	80+	120V	25,000	E26	75W	3	★
09160	LED11WPAR30/NFL/840K-DIM-G6	850	11W	4000K	80+	120V	25,000	E26	75W	3	★
09480	LED12WPAR30S/NFL/830-DIM-G7	950	12W	3000K	80+	120V	25,000	E26	75W	4	
09481	LED12WPAR30S/NFL/840-DIM-G7	950	12W	4000K	80+	120V	25,000	E26	75W	4	
09476	LED12WPAR30S/FL/827-DIM-G7	950	12W	2700K	80+	120V	25,000	E26	75W	4	★
09477	LED12WPAR30S/FL/830-DIM-G7	950	12W	3000K	80+	120V	25,000	E26	75W	4	★
09478	LED12WPAR30S/FL/840-DIM-G7	950	12W	4000K	80+	120V	25,000	E26	75W	4	★
09479	LED12WPAR30S/NFL/827-DIM-G7	950	12W	2700K	80+	120V	25,000	E26	75W	4	★
08557	LED12WPAR30S/NFL/830-DIM-G4A	850	12W	3000K	80+	120V	25,000	E26	75W	4	
08558	LED12WPAR30S/NFL/840-DIM-G4A	850	12W	4000K	80+	120V	25,000	E26	75W	4	
09161	LED13WPAR38/FL/827K-DIM-G6	1,050	13W	2700K	80+	120V	25,000	E26	100W	5	★
09162	LED13WPAR38/FL/830K-DIM-G6	1,050	13W	3000K	80+	120V	25,000	E26	100W	5	★
09163	LED13WPAR38/FL/840K-DIM-G6	1,050	13W	4000K	80+	120V	25,000	E26	100W	5	★
09165	LED13WPAR38/NFL/830K-DIM-G6	1,050	13W	3000K	80+	120V	25,000	E26	100W	5	
09990	LED15WPAR38/FL/830-DIM-G8	1,250	15W	3000K	80+	120V	25,000	E26	120W	5	
09991	LED15WPAR38/FL/840-DIM-G8	1,250	15W	4000K	80+	120V	25,000	E26	120W	5	
09992	LED15WPAR38/FL/850-DIM-G8	1,250	15W	5000K	80+	120V	25,000	E26	120W	5	
09513	LED15WPAR38/FL/827-DIM-G7	1,250	15W	2700K	80+	120V	25,000	E26	120W	5	★
09514	LED15WPAR38/FL/830-DIM-G7	1,250	15W	3000K	80+	120V	25,000	E26	120W	5	★
09515	LED15WPAR38/FL/840-DIM-G7	1,250	15W	4000K	80+	120V	25,000	E26	120W	5	★
09516	LED15WPAR38/FL/850-DIM-G7	1,250	15W	5000K	80+	120V	25,000	E26	120W	5	★
09730	LED15WPAR38/NFL/840-DIM-G7	1,300	15W	4000K	80+	120V	25,000	E26	120W	5	
09170	LED20WPAR38/FL/827K-DIM-G6	1,700	20W	2700K	80+	120V	25,000	E26	150W	6	★
09171	LED20WPAR38/FL/830K-DIM-G6	1,700	20W	3000K	80+	120V	25,000	E26	150W	6	★
09172	LED20WPAR38/FL/840K-DIM-G6	1,700	20W	4000K	80+	120V	25,000	E26	150W	6	★





MR Replacement Lamps

- Direct replacement for halogen miniature reflector lamps
- 25,000 hour rated life lasting 20x longer than halogen incandescent
- Choice of 2700K, 3000K and 4000K CCT
- Available in 2 beam distributions: 25° Narrow Flood & 40° Flood
- Shatter-resistant for reduced risk of injury or breakage
- Contains no lead or mercury; RoHS compliant

LitespanLED® MR Lamps

Order Code	Item	Lm	W	CCT	CRI	V	Life/Hrs L70	Base	Replaces Incan.	Photo #	ES
08893	LED2WMR11/120/830-G5	140	3W	3000K	80+	12V	35,000	GU4	20W	1	
10039	LED4WMR11/120/830-G8	260	4W	3000K	80+	12V	35,000	GU4	20W	1	
10040	LED4WMR11/120/840-G8	260	4W	4000K	80+	12V	35,000	GU4	20W	1	
08894	LED4WMR11/120/830-G5	160	4W	3000K	80+	12V	35,000	GU4	20W	1	
09204	LED7WMR16/NFL/827K-DIM-G6	400	7W	2700K	80+	12V	25,000	GU5.3	50W	3	
08834	LED7WMR16/20/830-G5	400	7W	3000K	80+	12V	25,000	GU5.3	50W	3	
08837	LED7WMR16/40/840-G5	400	7W	4000K	80+	12V	25,000	GU5.3	50W	3	
09494	LED7WMR16/FL/830-DIM-G7	500	7W	3000K	80+	12V	25,000	GU5.3	50W	3	★
09493	LED7WMR16/FL/827-DIM-G7	500	7W	2700K	80+	12V	25,000	GU5.3	50W	3	★
09495	LED7WMR16/FL/840-DIM-G7	500	7W	4000K	80+	12V	25,000	GU5.3	50W	3	★
09543	LED7WMR16/NFL/827-DIM-G7	500	7W	2700K	80+	12V	25,000	GU5.3	50W	3	★
09544	LED7WMR16/NFL/830-DIM-G7	500	7W	3000K	80+	12V	25,000	GU5.3	50W	3	★
09545	LED7WMR16/NFL/840-DIM-G7	500	7W	4000K	80+	12V	25,000	GU5.3	50W	3	★
09496	LED7WGU10/FL/827-DIM-G7	500	7W	2700K	80+	12V	25,000	GU10	50W	2	★
09497	LED7WGU10/FL/830-DIM-G7	500	7W	3000K	80+	12V	25,000	GU10	50W	2	★
10011	LED7WGU10/FL/830-DIM-G8	500	7W	3000K	80+	12V	25,000	GU10	50W	2	
09988	LED7WGU10/NFL/827-DIM-G8	500	7W	2700K	80+	120V	25,000	GU10	50W	2	
10013	LED7WGU10/NFL/830-DIM-G8	500	7W	3000K	80+	12V	25,000	GU10	50W	2	
09989	LED7WGU10/NFL/840-DIM-G8	500	7W	4000K	80+	120V	25,000	GU10	50W	2	
90028	LED7WGU10/20/830-DIM-G4	450	7W	3000K	80+	120V	25,000	GU10	45W	2	
09498	LED7WGU10/FL/840-DIM-G7	500	7W	4000K	80+	120V	25,000	GU10	50W	2	
09546	LED7WGU10/NFL/827-DIM-G7	500	7W	2700K	80+	120V	25,000	GU10	50W	2	★
09547	LED7WGU10/NFL/830-DIM-G7	500	7W	3000K	80+	120V	25,000	GU10	50W	2	



5 YEAR WARRANTY



LitespanLED® Elevator Lights

Order Code	Item	Lm	W	CCT	CRI	V	Life/Hrs L70	Base	Replaces Incan.	Photo #	ES
08895	LED3WGBF/30/830-G5	125	3W	3000K	80+	12V	20,000	BA15d	GBF	4	
08900	LED3WGBF/30/840-G5	125	3W	4000K	75	12V	20,000	BA15d	GBF	4	
08896	LED3W1383/30/830-G5	125	3W	3000K	80+	12V	20,000	BA15s	1383	5	
08899	LED3W1383/30/840-G5	125	3W	4000K	75	12V	20,000	BA15s	1383	5	





Decorative Replacement Lamps

- Direct replacement for incandescent globe and bullet lamps
- 15,000 hour rated life
- 50,000 hour design life
- Ideal for wall sconces and ceiling fans
- Available in 2700K, 3000K and 4000K CCT
- Lasts 10x longer than incandescent
- Instant-on with no warm up, unlike CFLs
- Not for use in enclosed fixtures


LitespanLED® Decorative

Order Code	Item	Lm	W	CCT	CRI	V	Life/Hrs L70	Base	Replaces Incan.	Photo #	ES
09995	LED6WG25/840-DIM-G8	450	6W	4000K	80+	120V	15,000	E26	40W	1	
90038	LED6WG25/827K-DIM-G4	450	6W	2700K	80+	120V	15,000	E26	40W	1	★
90037	LED6WG25/830K-DIM-G4	450	6W	3000K	80+	120V	15,000	E26	40W	1	★
90036	LED6WG25/840K-DIM-G4	450	6W	4000K	80+	120V	15,000	E26	40W	1	
10007	LED5WB11/E12/827-DIM-G8	350	4.5W	2700K	80+	120V	25,000	E12	40W	2	
10008	LED5WB11/E12/830-DIM-G8	350	4.5W	3000K	80+	120V	25,000	E12	40W	2	
08729	LED5WB11/E12/827-DIM-G5	325	5W	2700K	80+	120V	25,000	E12	40W	2	★
08730	LED5WB11/E12/830-DIM-G5	325	5W	3000K	80+	120V	25,000	E12	40W	2	★
08731	LED5WB11/E26/827-DIM-G5	325	5W	2700K	80+	120V	25,000	E26	40W	3	★
08732	LED5WB11/E26/830-DIM-G5	325	5W	3000K	80+	120V	25,000	E26	40W	3	★



5 YEAR WARRANTY





G4 & G9 Replacement Lamps

- Direct replacement for halogen incandescent G4 & G9 lamps
- Consumes 75% less energy and lasts 25x longer than incandescent bulbs
- 25,000 hour rated life
- Choice of 3000K, 4000K, and 5000K CCT
- 200° multi-directional beam angle
- Integrated driver

LitespanLED® Landscape Replacement LED Lamps

Order Code	Item	Lm	W	CCT	CRI	V	Life/Hrs L70	Base	Replaces Incan.	Photo #	ES
10041	LED2WG4/830-G8	250	2.5W	3000K	80+	12V	25,000	G4	10W	1	
10042	LED2WG4/840-G8	250	2.5W	4000K	80+	12V	25,000	G4	10W	1	
08606	LED2WG4/840K-G4	200	3W	4000K	80+	12V	25,000	G4	10W	1	
08607	LED2WG4/850K-G4	200	3W	5000K	80+	12V	25,000	G4	10W	1	
10043	LED2WG9/830-G8	250	2.5W	3000K	80+	120V	25,000	G9	10W	2	
10044	LED2WG9/840-G8	250	2.5W	4000K	80+	120V	25,000	G9	10W	2	
08610	LED2WG9/850K-G4	200	3W	5000K	80+	120V	25,000	G9	10W	2	



5 YEAR WARRANTY





High Bay Fixtures

- Cost-effective, solid-state solutions for highbay and lowbay applications
- Replaces high-watt HID fixtures and/or multi-lamp fluorescent luminaires
- Available in round and linear configurations
- Range of available accessories to customize fixtures to individual needs
- 5 year system warranty

BAY : Round Bay Light

Order Code	Item	Lm	W	CCT	CRI	V	Life/Hrs L70	MOL	Dim	Replaces Fluor.	Photo #	DLC
09796	BAY-3C-40K-U	12,500	100W	4000K	80+	100~277V	50,000	11.8"	1-10V	150W-175W	1	✓
09797	BAY-3C-40K-V	12,500	100W	4000K	80+	200~480V	50,000	11.8"	1-10V	150W-175W	1	✓
09582	BAY-3C-50K-U	12,500	100W	5000K	80+	100~277V	50,000	11.8"	1-10V	150W-175W	1	✓
09588	BAY-3C-50K-V	12,500	100W	5000K	80+	200~480V	50,000	11.8"	1-10V	150W-175W	1	✓
09798	BAY-4C-40K-U	18,750	150W	4000K	80+	100~277V	50,000	11.8"	1-10V	250W-320W	1	✓
09799	BAY-4C-40K-V	18,750	150W	4000K	80+	200~480V	50,000	11.8"	1-10V	250W-320W	1	✓
09583	BAY-4C-50K-U	18,750	150W	5000K	80+	100~277V	50,000	11.8"	1-10V	250W-320W	1	✓
09589	BAY-4C-50K-V	18,750	150W	5000K	80+	200~480V	50,000	11.8"	1-10V	250W-320W	1	✓
09800	BAY-5C-40K-U	25,000	200W	4000K	80+	100~277V	50,000	11.8"	1-10V	320W-400W	1	✓
09801	BAY-5C-40K-V	25,000	200W	4000K	80+	200~480V	50,000	11.8"	1-10V	320W-400W	1	✓
09584	BAY-5C-50K-U	25,000	200W	5000K	80+	100~277V	50,000	11.8"	1-10V	320W-400W	1	✓
09590	BAY-5C-50K-V	25,000	200W	5000K	80+	200~480V	50,000	11.8"	1-10V	320W-400W	1	✓

BAY : Accessories

Order Code	Item	Description	Order Code	Item	Description
09585	BAY-REFLECTOR BT-AL-60D	60° Aluminum Reflector	09910	BAY-SEN-1A-KIT	Occupancy / Photocontrol Sensor Kit, Remote Controllable
09586	BAY-REFLECTOR BT-AL-90D	90° Aluminum Reflector	09912	BAY-WG-AL	Wire Guard, Aluminum Reflector
09587	BAY-REFLECTOR BT-PC-70D	70° Polycarbonate Reflector	09913	BAY-WG-GL	Wire Guard, Glass
09914	BAY-REFLECTOR-CV16	Cloudveil Reflector, 16" for BAY	09911	BAY-WG-PC	Wire Guard, PC Reflector
09915	BAY-REFLECTOR-CV22	Cloudveil Reflector, 22" for BAY			



LLH : Linear High Bay

Order Code	Item	Lm	W	CCT	CRI	V	Life/Hrs L70	Dim	Replaces Fluor.	Photo #	DLC Premium
09703	LLH-1C-40K-U	14,300	110W	4000K	80+	120~277V	50,000	0-10V	HBF 6lamp T8 / 4lamp T5	2	✓✓
09793	LLH-1C-40K-V	14,300	110W	4000K	80+	347~480V	50,000	0-10V	HBF 6lamp T8 / 4lamp T5	2	✓✓
09538	LLH-1C-50K-U	14,410	107W	5000K	80+	120~277V	50,000	0-10V	HBF 6lamp T8 / 4lamp T5	2	✓✓
09571	LLH-1C-50K-U-1S	14,410	110W	5000K	80+	120~277V	50,000	0-10V	HBF 6lamp T8 / 4lamp T5	2	✓✓
09741	LLH-1C-50K-V	14,300	110W	5000K	80+	347~480V	50,000	0-10V	HBF 6lamp T8 / 4lamp T5	2	✓✓
09771	LLH-2C-40K-U	21,060	162W	4000K	80+	120~277V	50,000	0-10V	HBF 8lamp T8 / 6lamp T5 HO	2	✓✓
09794	LLH-2C-40K-V	21,060	162W	4000K	80+	347~480V	50,000	0-10V	HBF 8lamp T8 / 6lamp T5 HO	2	✓✓
09539	LLH-2C-50K-U	21,222	160W	5000K	80+	120~277V	50,000	0-10V	HBF 8lamp T8 / 6lamp T5 HO	2	✓✓
09572	LLH-2C-50K-U-1S	21,222	162W	5000K	80+	120~277V	50,000	0-10V	HBF 8lamp T8 / 6lamp T5 HO	2	✓✓
09742	LLH-2C-50K-V	21,222	162W	5000K	80+	347~480V	50,000	0-10V	HBF 8lamp T8 / 6lamp T5 HO	2	✓✓
09772	LLH-3C-40K-U	28,990	223W	4000K	80+	120~277V	50,000	0-10V	8 Lamp T5 HO	3	✓✓
09540	LLH-3C-50K-U	29,213	214W	5000K	80+	120~277V	50,000	0-10V	8 Lamp T5 HO	3	✓✓
09573	LLH-3C-50K-U-1S	29,213	223W	5000K	80+	120~277V	50,000	0-10V	8 Lamp T5 HO	3	✓✓
09922	LLH-3C-50K-U-1S-EM/25W	29,000	223W	5000K	80+	120~277V	50,000	0-10V	8 Lamp T5 HO	3	
09937	LLH-3C-50K-U-EM/25W	29,000	223W	5000K	80+	120~277V	50,000	0-10V	8 Lamp T5 HO	3	
09591	LLH-3C-50K-V	28,990	223W	5000K	80+	347~480V	50,000	0-10V	8 Lamp T5 HO	3	✓✓
09541	LLH-4C-50K-U	34,715	265W	5000K	80+	120~277V	50,000	0-10V	8 Lamp T5 HO	3	✓✓
09774	LLH-5C-40K-U	41,920	321W	4000K	80+	120~277V	50,000	0-10V	8 Lamp T5 HO	3	✓✓
09542	LLH-5C-50K-U	41,920	314W	5000K	80+	120~277V	50,000	0-10V	8 Lamp T5 HO	3	✓✓
09592	LLH-5C-50K-V	41,920	320W	5000K	80+	347~480V	50,000	0-10V	8 Lamp T5 HO	3	✓✓

LLH : Accessories

Order Code	Item	Description
09226	LLH-CHAIN	Mounting Chain for LLH, 1.05 meters (1 pair)
09227	LLH-PENDANT BOX	Pendant Box for LLH, 3/4 inch NPT
09230	LLH-V HOOK-1	V-Hook for LLH-2C-U, LLH-4C-U, LLH-1C-XXK-U, LLH-3C-XXK-U
09229	LLH-V HOOK-1.5	V-Hook for LLH-3C-U, LLH-2C-XXK-U, LLH-4C-XXK-U, LLH-5C-XXK-U
09336	LLH-CL-2X1	Clear Lens for LLH-2C-U, LLH-1C-XXK-U
09337	LLH-CL-2X1.5	Clear Lens for LLH-3C-U, LLH-2C-XXK-U
09338	LLH-CL-4X1	Clear Lens for LLH-4C-U, LLH-3C-XXK-U
09339	LLH-FL-2X1	Frosted Lens for LLH-2C-U, LLH-1C-XXK-U
09340	LLH-FL-2X1.5	Frosted Lens for LLH-3C-U, LLH-2C-XXK-U
09341	LLH-FL-4X1	Frosted Lens for LLH-4C-U, LLH-3C-XXK-U
09222	LLH-WG-2X1	Wireguard for LLH-2C-U, LLH-1C-XXK-U
09223	LLH-WG-2X1.5	Wireguard for LLH-3C-U, LLH-2C-XXK-U
09224	LLH-WG-4X1	Wireguard for LLH-4C-U, LLH-3C-XXK-U
09700	LLH-CL-4X1.5	Clear Lens for LLH-4C-XXK-U, LLH-5C-XXK-U
09701	LLH-FL-4X1.5	Frosted Lens for LLH-4C-XXK-U, LLH-5C-XXK-U
09702	LLH-WG-4X1.5	Wire Guard for LLH-4C-XXK-U, LLH-5C-XXK-U
09818	LLH-SMK-1	Surface Mount Kit, 12.6 Inches
09819	LLH-SMK-2	Surface Mount Kit, 17.3 Inches





Linear Fixtures

- Cost-effective, energy-efficient replacements for fluorescent linear fixtures
- Durable and stylish construction
- Available in 4000K and 5000K color temperature
- Dimmable
- 5 year system warranty

LLW : Linear Wrap

Order Code	Item	Size	Lm	W	CCT	CRI	V	Life/Hrs L70	Dim	Photo #	DLC Premium
09704	LLW-4CP-40K-U	4'	4,420	34W	4000K	80+	120~277V	50,000	0-10V	1	✓✓
09426	LLW-4C-40K-U	4'	4,608	36W	4000K	85+	120~277V	50,000	0-10V	1	✓✓
09705	LLW-5CP-40K-U	4'	5,200	40W	4000K	80+	120~277V	50,000	0-10V	1	✓✓

LLW : Accessories

Order Code	Item	Description
09844	LLW-LENS	Replacement Lens for LLW Fixtures

STR : Linear Strip

Order Code	Item	Size	Lm	W	CCT	CRI	V	Life/Hrs L70	Dim	Photo #	DLC Premium
09534	STR-2C-40K-U	4'	3,013	23W	4000K	80+	120~277V	50,000	0-10V	2	✓✓
09820	STR-2C-50K-U	4'	3,013	23W	5000K	80+	120~277V	50,000	0-10V	2	✓✓
09535	STR-3C-40K-U	4'	4,224	32W	4000K	80+	120~277V	50,000	0-10V	2	✓✓
09821	STR-3C-50K-U	4'	4,224	32W	5000K	80+	120~277V	50,000	0-10V	2	✓✓
09536	STR-4C-40K-U	4'	6,026	46W	4000K	80+	120~277V	50,000	0-10V	2	✓✓
09822	STR-4C-50K-U	4'	6,026	46W	5000K	80+	120~277V	50,000	0-10V	2	✓✓

STR : Accessories

Order Code	Item	Description
09788	STR-4-WG-W	Wire Guard, 4 ft. LED Strip, White
09823	STR-LCK	LED Strip, Linear Connection Kit
09843	STR-LENS	Replacement Lens for STR Fixtures



5 YEAR WARRANTY

UL US LISTED



VTS : Vapor Tight

Order Code	Item	Lm	W	CCT	CRI	V	Life/Hrs L70	MOL	Dim	Replaces Fluor.	Photo #	DLC Premium
09979	VTS-4-45/B0/850-DIM-U	4,500	40W	5000K	80+	120~277V	50,000	50.24"	0-10V	(2) F32T8	3	✓✓
09977	VTS-4-52/D0/850-DIM-U	5,200	40W	5000K	80+	120~277V	50,000	50.24"	0-10V	(2) F32T8	3	✓✓
09978	VTS-4-68/D0/850-DIM-U	6,800	52W	5000K	80+	120~277V	50,000	50.24"	0-10V	(2) F32T8	3	✓✓
09980	VTS-4-75/B5/850-DIM-U	7,500	65W	5000K	80+	120~277V	50,000	50.24"	0-10V	(2) F32T8	3	✓✓
09712	VTS-5CP-40K-U	5,200	40W	4000K	80+	120~277V	50,000	50.24"	0-10V	(2) F32T8	4	✓✓
09714	VTS-4CS-40K-U	4,400	40W	4000K	80+	120~277V	50,000	50.24"	0-10V	(2) F32T8	4	✓✓
09713	VTS-7CP-40K-U	6,760	52W	4000K	80+	120~277V	50,000	50.24"	0-10V	(2) F54T5HO	4	✓✓
09715	VTS-7CS-40K-U	7,150	65W	4000K	80+	120~277V	50,000	50.24"	0-10V	(2) F54T5HO	4	✓✓

VTS : Accessories

Order Code	Item	Description
09845	VTS-LENS	Replacement Lens for VTS-1C-U and VTS-2C-U





Troffer & Panel Fixtures

- Alternative LED solution to traditional fluorescent troffers
- Ultra-high-efficiency LEDs provide superior performance
- Choice of 3500K, 4000K, or 5000K
- Available in 2'x2' and 2'x4'
- Standard 0-10V dimming driver
- Universal input voltage (120-277V)
- 5 year system warranty

VOL : Volumetric Troffer

Order Code	Item	Size	Lm	W	CCT	CRI	V	Life/Hrs L70	Dim	Replaces Fluor.	Photo #	DLC Premium
09469	VOL22-3C-35K-U	2'x2'	3,275	26W	3500K	80+	120V	50,000	0-10V	3x 17WT8, 2U31T8	1	✓✓
09470	VOL22-3C-40K-U	2'x2'	3,275	26W	4000K	80+	120V	50,000	0-10V	3x 17WT8, 2U31T8	1	✓✓
09491	VOL22-3C-50K-U	2'x2'	3,275	26W	5000K	80+	120V	50,000	0-10V	3x 17WT8, 2U31T8	1	✓✓
09706	VOL22-3CP-35K-U	2'x2'	3,224	26W	3500K	80+	120~277V	50,000	0-10V	3x 17WT8, 2U31T8	1	✓✓
09707	VOL22-3CP-40K-U	2'x2'	3,250	26W	4000K	80+	120~277V	50,000	0-10V	3x 17WT8, 2U31T8	1	✓✓
09708	VOL22-3CP-50K-U	2'x2'	3,276	26W	5000K	80+	120~277V	50,000	0-10V	3x 17WT8, 2U31T8	1	✓✓
09709	VOL24-5CP-35K-U	2'x4'	5,796	46W	3500K	80+	120~277V	50,000	0-10V	2x 32T8, 3x 32T8	2	✓✓
09710	VOL24-5CP-40K-U	2'x4'	5,796	46W	4000K	80+	120~277V	50,000	0-10V	2x 32T8, 3x 32T8	2	✓✓
09711	VOL24-5CP-50K-U	2'x4'	5,796	46W	5000K	80+	120~277V	50,000	0-10V	2x 32T8, 3x 32T8	2	✓✓
09471	VOL24-5C-35K-U	2'x4'	5,750	48W	3500K	80+	120V	50,000	0-10V	2x 32T8, 3x 32T8	2	✓✓
09492	VOL24-5C-50K-U	2'x4'	5,842	48W	5000K	80+	120V	50,000	0-10V	2x 32T8, 3x 32T8	2	✓✓

VOL : Accessories

Order Code	Item	Description
09898	VOL-22-SMK-W	Volumetric Troffer, 2x2 Surface Mount Kit, White
09899	VOL-24-SMK-W	Volumetric Troffer, 2x4 Surface Mount Kit, White
09950	VOL22-LENS	Replacement Lens for VOL22 Fixtures
09951	VOL24-LENS	Replacement Lens for VOL24 Fixtures




SLM : Slim Panel

Order Code	Item	Size	Lm	W	CCT	CRI	V	Life/Hrs L70	Dim	Replaces Fluor.	Photo #	DLC/Premium
09760	SLM14-4CB-35K-U	1'x4'	3,750	30W	3500K	80+	100~277V	50,000	0-10V	3x 17WT8, 2U31T8	3	✓✓
09761	SLM14-4CB-40K-U	1'x4'	3,750	30W	4000K	80+	100~277V	50,000	0-10V	3x 17WT8, 2U31T8	3	✓✓
09762	SLM14-4CB-50K-U	1'x4'	3,750	30W	5000K	80+	100~277V	50,000	0-10V	3x 17WT8, 2U31T8	3	✓✓
09485	SLM22-3C-35K-U	2'x2'	3,000	30W	3500K	80+	100~277V	50,000	0-10V	3x 17WT8, 2U31T8	4	✓
09486	SLM22-3C-40K-U	2'x2'	3,000	30W	4000K	80+	100~277V	50,000	0-10V	3x 17WT8, 2U31T8	4	✓
09487	SLM22-3C-50K-U	2'x2'	3,000	30W	5000K	80+	100~277V	50,000	0-10V	3x 17WT8, 2U31T8	4	✓
10015	SLM22-3CB-35K-U	2'x2'	3,000	30W	3500K	80+	100~277V	50,000	0-10V	3x 17WT8, 2U31T8	4	✓✓
10016	SLM22-3CB-40K-U	2'x2'	3,000	30W	4000K	80+	100~277V	50,000	0-10V	3x 17WT8, 2U31T8	4	✓✓
10017	SLM22-3CB-50K-U	2'x2'	3,000	30W	5000K	80+	100~277V	50,000	0-10V	3x 17WT8, 2U31T8	4	✓✓
09763	SLM22-4CB-35K-U	2'x2'	3,750	30W	3500K	80+	100~277V	50,000	0-10V	3x 17WT8, 2U31T8	4	✓✓
09764	SLM22-4CB-40K-U	2'x2'	3,750	30W	4000K	80+	100~277V	50,000	0-10V	3x 17WT8, 2U31T8	4	✓✓
09765	SLM22-4CB-50K-U	2'x2'	3,750	30W	5000K	80+	100~277V	50,000	0-10V	3x 17WT8, 2U31T8	4	✓✓
09754	SLM22-5CB-35K-U	2'x2'	5,000	40W	3500K	80+	100~277V	50,000	0-10V	3x 17WT8, 2U31T8	4	✓✓
09755	SLM22-5CB-40K-U	2'x2'	5,000	40W	4000K	80+	100~277V	50,000	0-10V	3x 17WT8, 2U31T8	4	✓✓
09756	SLM22-5CB-50K-U	2'x2'	5,000	40W	5000K	80+	100~277V	50,000	0-10V	3x 17WT8, 2U31T8	4	✓✓
10018	SLM24-4CB-35K-U	2'x4'	4,000	40W	3500K	80+	100~277V	50,000	0-10V	2x 32T8, 3x 32T8	5	✓✓
10019	SLM24-4CB-40K-U	2'x4'	4,000	40W	4000K	80+	100~277V	50,000	0-10V	2x 32T8, 3x 32T8	5	✓✓
10021	SLM24-4CB-50K-U	2'x4'	4,000	40W	5000K	80+	100~277V	50,000	0-10V	2x 32T8, 3x 32T8	5	✓✓
09488	SLM24-5C-35K-U	2'x4'	4,000	40W	3500K	80+	100~277V	50,000	0-10V	2x 32T8, 3x 32T8	5	✓
09489	SLM24-5C-40K-U	2'x4'	4,000	40W	4000K	80+	100~277V	50,000	0-10V	2x 32T8, 3x 32T8	5	✓
09490	SLM24-5C-50K-U	2'x4'	4,000	40W	5000K	80+	100~277V	50,000	0-10V	2x 32T8, 3x 32T8	5	✓
09766	SLM24-5CB-35K-U	2'x4'	5,000	40W	3500K	80+	100~277V	50,000	0-10V	2x 32T8, 3x 32T8	5	✓✓
09767	SLM24-5CB-40K-U	2'x4'	5,000	40W	4000K	80+	100~277V	50,000	0-10V	2x 32T8, 3x 32T8	5	✓✓
09768	SLM24-5CB-50K-U	2'x4'	5,000	40W	5000K	80+	100~277V	50,000	0-10V	2x 32T8, 3x 32T8	5	✓✓
09757	SLM24-6CB-35K-U	2'x4'	6,250	50W	3500K	80+	100~277V	50,000	0-10V	2x 32T8, 3x 32T8	5	✓✓
09758	SLM24-6CB-40K-U	2'x4'	6,250	50W	4000K	80+	100~277V	50,000	0-10V	2x 32T8, 3x 32T8	5	✓✓
09759	SLM24-6CB-50K-U	2'x4'	6,250	50W	5000K	80+	100~277V	50,000	0-10V	2x 32T8, 3x 32T8	5	✓✓

SLM : Accessories

Order Code	Item	Description
09692	SLM22-CABLE	SLM22 Cable Set, 4 Cables per Set
09693	SLM24-CABLE	SLM24 Cable Set, 6 Cables per Set
09905	SLM14-SM	SLM14 Surface Mount Kit White
09694	SLM22-SM	SLM22 Surface Mount Kit White
09695	SLM24-SM	SLM24 Surface Mount Kit White





Downlight Fixtures

- Ultra-efficient LED downlight kits designed to retrofit into existing incandescent recessed downlights
- Integrated LEDs reduce energy consumption up to 80%
- Fits many popular recessed downlight fixtures
- Lasts up to 30x longer than incandescent
- Choice of soft white, warm white and cool white CCT
- Instant-on, no warmup time
- 90 CRI versions available

DKDS : Downlight Disk Surface Kit

Order Code	Item	Size	Lm	W	CCT	CRI	V	Life/Hrs L70	Replaces	Photo #	ES
09916	DKDS-4-12W/6.5/927-DIM-120	4"	650	12W	2700K	90+	120~277V	54,000	65W BR	1	★
09917	DKDS-4-12W/6.5/930-DIM-120	4"	650	12W	3000K	90+	120~277V	54,000	65W BR	1	★
09920	DKDS-6-15W/9.5/927-DIM-120	6"	950	15W	2700K	90+	120~277V	54,000	65W BR	1	
09921	DKDS-6-15W/9.5/930-DIM-120	6"	950	15W	3000K	90+	120~277V	54,000	65W BR	1	

AK : Adjustable Neck Downlight

Order Code	Item	Size	Lm	W	CCT	CRI	V	Life/Hrs L70	Replaces	Photo #	ES
09524	AK4-8.5W827-DIM-G7 2PK	4"	500	9W	2700K	80+	120V	25,000	50W BR20	2	★
09525	AK6-12W827-DIM-G7 2PK	5"/6"	800	12W	2700K	80+	120V	25,000	65W BR30	2	★

CDR : Commercial Downlight Retrofit Kit

Order Code	Item	Size	Lm	W	CCT	CRI	V	Life/Hrs L70	Replaces	Photo #	ES
09234	CDR-3C-830K-U	6"	2,200	25W	3000K	80+	120~277V	54,000	(2) 18W CFL	3	★
09729	CDR-4C-830K-AL-U	8"	3,000	35W	3000K	80+	120~277V	54,000	(2) 26W CFL	3	
09240	CDR-5C-830K-U	10"	4,200	50W	3000K	80+	120~277V	54,000	(2) 42W CFL	3	★
09241	CDR-5C-835K-U	10"	4,200	50W	3500K	80+	120~277V	54,000	(2) 42W CFL	3	★
09242	CDR-5C-840K-U	10"	4,200	50W	4000K	80+	120~277V	54,000	(2) 42W CFL	3	★



DSK : Slim Disk Downlight

Order Code	Item	Size	Lm	W	CCT	CRI	V	Life/Hrs L70	Replaces	Photo #	ES
09518	DSK-11W927-DIM-G7	5"	650	11W	2700K	90+	120V	50,000	50W BR20	4	★
09519	DSK-11W930-DIM-G7	5"	650	11W	3000K	90+	120V	50,000	50W BR20	4	★
09520	DSK-11W940-DIM-G7	5"	650	11W	4000K	90+	120V	50,000	50W BR20	4	★
09521	DSK-15W927-DIM-G7	7"	850	15W	2700K	90+	120V	50,000	65W BR30	4	★
09522	DSK-15W930-DIM-G7	7"	850	15W	3000K	90+	120V	50,000	65W BR30	4	★
09523	DSK-15W940-DIM-G7	7"	850	15W	4000K	90+	120V	50,000	65W BR30	4	★

4" Downlight Kit

Order Code	Item	Lm	W	CCT	CRI	V	Life/Hrs L70	Replaces	Photo #	ES
09677	LED-DK4-9W927-DIM-G7	600	9W	2700K	90+	120V	50,000	65W BR	5	★
09678	LED-DK4-9W930-DIM-G7	600	9W	3000K	90+	120V	50,000	65W BR	5	★
09679	LED-DK4-9W940-DIM-G7	600	9W	4000K	90+	120V	50,000	65W BR	5	★
09680	LED-DK4-9W950-DIM-G7	600	9W	5000K	90+	120V	50,000	65W BR	5	★

4" Rotatable Downlight


Order Code	Item	Lm	W	CCT	CRI	V	Life/Hrs L70	Replaces	Photo #	ES
09083	LED-DK4RT-11W830-DIM-G5	650	11W	3000K	80+	120V	50,000	65W BR	6	★
09084	LED-DK4RT-11W840-DIM-G5	650	11W	4000K	80+	120V	50,000	65W BR	6	★

6" Downlight Kit

Order Code	Item	Lm	W	CCT	CRI	V	Life/Hrs L70	Replaces	Photo #	ES
09681	LED-DK6-11W927-DIM-G7	700	11W	2700K	90+	120V	50,000	65W BR	7	★
09682	LED-DK6-11W930-DIM-G7	700	11W	3000K	90+	120V	50,000	65W BR	7	★
09683	LED-DK6-11W940-DIM-G7	700	11W	4000K	90+	120V	50,000	65W BR	7	★
09684	LED-DK6-11W950-DIM-G7	700	11W	5000K	90+	120V	50,000	65W BR	7	★
09685	LED-DK6-15W927-DIM-G7	1,100	15W	2700K	90+	120V	50,000	65W BR	7	★
09686	LED-DK6-15W930-DIM-G7	1,100	15W	3000K	90+	120V	50,000	65W BR	7	★
09687	LED-DK6-15W940-DIM-G7	1,100	15W	4000K	90+	120V	50,000	65W BR	7	★
09688	LED-DK6-15W950-DIM-G7	1,100	15W	5000K	90+	120V	50,000	65W BR	7	★

6" Rotatable Downlight

Order Code	Item	Lm	W	CCT	CRI	V	Life/Hrs L70	Replaces	Photo #	ES
09085	LED-DK6RT-11W830-DIM-G5	750	11W	3000K	80+	120V	50,000	65W BR	8	★
09086	LED-DK6RT-11W840-DIM-G5	750	11W	4000K	80+	120V	50,000	65W BR	8	★





Outdoor Fixtures

- Cost-effective, solid-state LED solutions for flood and area lighting
- Replaces traditional HID or quartz halogen flood lights
- Instant-on with no warmup
- 5 year system warranty
- Long 50K+ hour life reduces maintenance costs

ASL : Area Site Lighter

Order Code	Item	Lm	W	CCT	CRI	V	Life/Hrs L70	Notes	Replaces HID	Photo #	DLC
09273	ASL-3C-40K-U	10,000	100W	4000K	70	120~277V	50,000	Type III, V	250W	1	✓
09274	ASL-3C-50K-U	10,000	100W	5000K	70	120~277V	50,000	Type III, V	250W	1	✓
09275	ASL-5C-40K-U	15,000	150W	4000K	70	120~277V	50,000	Type III, V	400W	1	✓
09276	ASL-5C-50K-U	15,000	150W	5000K	70	120~277V	50,000	Type III, V	400W	1	✓

ASL : Accessories

Order Code	Item	Description
09301	ASL-PM10	Pole Mount Arm, Square 10 Inch Bronze
09300	ASL-PM6	Pole Mount Arm, Square 6 Inch Bronze
09299	ASL-SF	Slipfitter 2-3/8 Inch Adjustable Bronze

FLJ : Floodlight

Order Code	Item	Lm	W	CCT	CRI	V	Life/Hrs L70	Notes	Replaces	Photo #	DLC
09619	FLJ-1C-30K-K-U	1,350	12W	3000K	80+	120~277V	50,000	Knuckle	150W	2	✓
09618	FLJ-1C-30K-Y-U	1,350	12W	3000K	80+	120~277V	50,000	Yoke	150W	3	✓
09612	FLJ-1C-50K-K-U	1,350	12W	5000K	80+	120~277V	50,000	Knuckle	150W	2	✓
09611	FLJ-1C-50K-Y-U	1,350	12W	5000K	80+	120~277V	50,000	Yoke	150W	3	✓
09614	FLJ-3C-30K-K-U	3,200	30W	3000K	80+	120~277V	50,000	Knuckle	300W	4	✓
09613	FLJ-3C-30K-Y-U	3,200	30W	3000K	80+	120~277V	50,000	Yoke	300W	5	✓
09623	FLJ-3C-50K-K-U	3,200	30W	5000K	80+	120~277V	50,000	Knuckle	300W	4	✓
09615	FLJ-3C-50K-Y-U	3,200	30W	5000K	80+	120~277V	50,000	Yoke	300W	5	✓

Continued on next page >>>



5 YEAR WARRANTY

UL US LISTED



FLJ : Floodlight

Order Code	Item	Lm	W	CCT	CRI	V	Life/Hrs L70	Notes	Replaces	Photo #	DLC
09621	FLJ-5C-30K-K-U	5,400	50W	3000K	80+	120~277V	50,000	Knuckle	300W	6	✓
09620	FLJ-5C-30K-Y-U	5,400	50W	3000K	80+	120~277V	50,000	Yoke	300W	7	✓
09617	FLJ-5C-50K-K-U	5,400	50W	5000K	80+	120~277V	50,000	Knuckle	300W	6	✓
09616	FLJ-5C-50K-Y-U	5,400	50W	5000K	80+	120~277V	50,000	Yoke	300W	7	✓





Wallpack Fixtures

- Economical and energy-efficient solutions for general purpose wall mount lighting
- Durable, impact-resistant construction
- Easy to install
- 5 year system warranty

DTD : Dusk to Dawn

Order Code	Item	Lm	W	CCT	CRI	V	Life/Hrs L70	Notes	Replaces HID	Photo #	DLC
09579	DTD-2C-50K-U	5,000	50W	5000K	80+	100~277V	50,000	w/ 120-277V photocell	175-250W	1	✓
09964	DTD-95/CO/850-DIM-GY-U	9,500	80W	5000K	80+	100~277V	50,000	w/ 120-277V photocell	400W	N/A	
09965	DTD-140/B5/850-DIM-GY-U	14,000	120W	5000K	80+	100~277V	50,000	w/ 120-277V photocell	400W	N/A	

WFA : Wallpack Flood ARCH

Order Code	Item	Lm	W	CCT	CRI	V	Life/Hrs L70	Notes	Replaces	Photo #	DLC
08597	WFAM-1C-U	1,600	22W	5000K	75	120~277V	50,000	Medium	70-150W	2	✓
08598	WFAM-2C-U	3,100	40W	5000K	75	120~277V	50,000	Medium	175-250W	2	
08599	WFAL-3C-U	7,100	90W	5000K	70	120~277V	50,000	Large	400W	3	

WFA : Accessories

Order Code	Item	Description
08738	PCB1	Photocontrol 120V
08706	WFAL-SF	2-3/8" Slipfitter
08707	WFAL-UT	U-Bracket
08705	WFAM-UT	U-Bracket



5 YEAR WARRANTY

UL US LISTED



WMC : Wallpack Cube

Order Code	Item	Lm	W	CCT	CRI	V	Life/Hrs L70	Finish	Photo #	DLC
09810	WMC-2C-40K-U	1,900	20W	4000K	80+	120~277V	50,000	Bronze	4	✓
09580	WMC-2C-50K-U	1,900	20W	5000K	80+	120~277V	50,000	Bronze	4	✓
09811	WMC-3C-40K-U	2,850	30W	4000K	80+	120~277V	50,000	Bronze	4	✓
09581	WMC-3C-50K-U	2,850	30W	5000K	80+	120~277V	50,000	Bronze	4	✓

WMG : Wallpack Glass

Order Code	Item	Lm	W	CCT	CRI	V	Life/Hrs L70	Finish	Photo #	DLC
09802	WMG-1C-40K-U	3,200	30W	4000K	70+	100~277V	50,000	Bronze	5	✓
09574	WMG-1C-50K-U	3,200	30W	5000K	70+	100~277V	50,000	Bronze	5	✓
09803	WMG-2C-40K-U	5,800	50W	4000K	70+	100~277V	50,000	Bronze	6	✓
09807	WMG-2C-40K-V	4,600	40W	4000K	70+	347~480V	50,000	Bronze	6	✓
09575	WMG-2C-50K-U	5,800	50W	5000K	70+	100~277V	50,000	Bronze	6	✓
09596	WMG-2C-50K-V	4,600	40W	5000K	70+	347~480V	50,000	Bronze	6	✓
09804	WMG-3C-40K-U	7,000	60W	4000K	70+	100~277V	50,000	Bronze	6	✓
09576	WMG-3C-50K-U	7,000	60W	5000K	70+	100~277V	50,000	Bronze	6	✓
09805	WMG-4C-40K-U	9,800	80W	4000K	70+	100~277V	50,000	Bronze	6	✓
09808	WMG-4C-40K-V	9,500	80W	4000K	70+	347~480V	50,000	Bronze	6	✓
09577	WMG-4C-50K-U	9,800	80W	5000K	70+	100~277V	50,000	Bronze	6	✓
09809	WMG-4C-50K-V	9,500	80W	5000K	70+	347~480V	50,000	Bronze	6	✓
09806	WMG-5C-40K-U	13,000	120W	4000K	70+	100~277V	50,000	Bronze	6	✓
09578	WMG-5C-50K-U	13,000	120W	5000K	70+	100~277V	50,000	Bronze	6	✓

WPT : Wallpack Trapezoid

Order Code	Item	Lm	W	CCT	CRI	V	Life/Hrs L70	Replaces HID	Photo #	DLC
09812	WPT1-55/840-BZ-U	5,500	50W	4000K	80+	120~277V	50,000	175-250W	11	✓
09813	WPT1-55/850-BZ-U	5,500	50W	5000K	80+	120~277V	50,000	175-250W	11	✓
09814	WPT1-88/840-BZ-U	8,800	80W	4000K	80+	120~277V	50,000	250-400W	11	✓
09816	WPT1-88/840-BZ-V	8,800	80W	4000K	80+	347~480V	50,000	250-400W	11	✓
09815	WPT1-88/850-BZ-U	8,800	80W	5000K	80+	120~277V	50,000	250-400W	11	✓
09817	WPT1-88/850-BZ-V	8,800	80W	5000K	80+	347~480V	50,000	250-400W	11	✓
08595	WPT-1C-U	2,900	37W	5000K	70	120~277V	50,000	175-250W	11	

WPW : Wallpack Wedge

Order Code	Item	Lm	W	CCT	CRI	V	Life/Hrs L70	Finish	Photo #	DLC
08589	WPW-1C-120	800	11W	5000K	70	120V	50K	Bronze	12	





Canopy Fixtures

- Cost-effective, solid-state solutions for canopy applications
- Replaces high-watt HID fixtures and/or fluorescent luminaires
- Available in round and square configurations
- 5 year limited warranty

SCRG : Surface Canopy Round, Garage

Order Code	Item	Lm	W	CCT	CRI	V	Life/Hrs L70	Replaces HID	Photo #	DLC Premium
09959	SCRG-50/DO/840-DIM-U-S1B-W	5,000	38W	4000K	80+	120-277V	50,000	50-175W	1	✓✓
09955	SCRG-50/DO/840-DIM-U-W	5,000	38W	4000K	80+	120-277V	50,000	50-175W	1	✓✓
09960	SCRG-50/DO/850-DIM-U-S1B-W	5,000	38W	5000K	80+	120-277V	50,000	50-175W	1	✓✓
09956	SCRG-50/DO/850-DIM-U-W	5,000	38W	5000K	80+	120-277V	50,000	50-175W	1	✓✓
09961	SCRG-75/DO/840-DIM-U-S1B-W	8,000	61W	4000K	80+	120-277V	50,000	175-250W	1	
09957	SCRG-75/DO/840-DIM-U-W	8,000	61W	4000K	80+	120-277V	50,000	175-250W	1	
09962	SCRG-75/DO/850-DIM-U-S1B-W	8,000	61W	5000K	80+	120-277V	50,000	175-250W	1	
09958	SCRG-75/DO/850-DIM-U-W	8,000	61W	5000K	80+	120-277V	50,000	175-250W	1	

SCRG : Accessories

Order Code	Item	Description
09963	SCRG-3G-BRK	3G Rated Quick Mount Bracket
09909	SEN-S1-RC	Remote Control for S1A Sensors
09908	SEN-S1A-KO	Sensor, OCC/PC/RC, IP65, 1/2" knockout mount, remote controllable

SCSS : Surface Canopy Square

Order Code	Item	Size	Lm	W	CCT	CRI	V	Life/Hrs L70	Replaces HID	Photo #	DLC
09002	SCSL-1C-U	10.3"	3,906	40W	5000K	70+	120~277V	50,000	50-175W	3	✓
09746	SCSS-1C-50K-U	10.3"	4,803	40W	5000K	70	120~277V	50,000	50-175W	2	✓
09747	SCSS-2C-50K-U	14.0"	6,313	57W	5000K	70+	120~277V	50,000	175-250W	2	✓
09004	SCSS-2C-U	14.0"	5,524	58W	5100K	70+	120~277V	50,000	175-250W	2	✓



5 YEAR WARRANTY

cUL US LISTED

DLC OPLE LISTED PREMIUM

DLC OPLE LISTED

SCRS : Surface Canopy Round

Order Code	Item	Size	Lm	W	CCT	CRI	V	Life/Hrs L70	Replaces Metal Halide	Photo #	DLC
09422	SCRS-2C-U	11"	4,393	41W	5000K	70+	120~277V	50,000	100W	4	✓

SCST : Slim Canopy

Order Code	Item	Size	Lm	W	CCT	CRI	V	Life/Hrs L70	Replaces HID	Photo #	DLC
09675	SCST-4C-50K-U		12,955	130W	5000K	70+	100~277V	60,000	400W	5	✓
09952	SCST-140/B0/850-U-W		14,000	127W	5000K	80+	120~277V	60,000		5	
09953	SCST-140/B0/850-V-W		14,000	127W	5000K	80+	120~277V	60,000		5	
09954	SCST-160/B0/850-U-W		16,000	145W	5000K	80+	120~277V	60,000		5	

SCST : Accessories

Order Code	Item	Description
09853	SCST-JBOX	Kit, Junction Box with 3/4 inch NPT Stem



Miniature LED

- 30,000 hour rated life
- Low power consumption and high brightness
- Direct replacement for standard incandescent lamps
- Available in blister pack, two per card
- Energy efficient: costs less than other alternatives to operate over the life of the lamp
- Extreme long life: less frequent re-lamping reduces maintenance costs



Order Code	Item	W	Life/ Hrs	Base	Color	Replaces Incandescent	Photo #
02678	LED-120-MB-G	110-130VAC	T-3¼	BA9s	Green	120MB, 120MB-6, 130MB, 8-3995, 949, 967	1
02679	LED-120-MB-R	110-130VAC	T-3¼	BA9s	Red	120MB, 120MB-6, 130MB, 8-3995, 949, 967	1
02681	LED-120-MB-W	110-130VAC	T-3¼	BA9s	White	120MB, 120MB-6, 130MB, 8-3995, 949, 967	1
02682	LED-120-MB-Y	110-130VAC	T-3¼	BA9s	Yellow	120MB, 120MB-6, 130MB, 8-3995, 949, 967	1
02683	LED-120-PSB-G	110-130VAC	T-2	TS5	Green	120PSB5, 120PSB-Neon	2
02684	LED-120-PSB-R	110-130VAC	T-2	TS5	Red	120PSB5, 120PSB-Neon	2
02685	LED-120-PSB-W	110-130VAC	T-2	TS5	White	120PSB5, 120PSB-Neon	2
02686	LED-120-PSB-Y	110-130VAC	T-2	TS5	Yellow	120PSB5, 120PSB-Neon	2
05379	LED-12-DCBAY-W	12VAC/DC	S-8	BAY15d	White	DC Index Bayonet Base 12V S8 Lamps	3
05385	LED-12-Festoon-W	12VAC/DC	Festoon 10mm	SV8.5mm	White	10 x 44 Xenon Festoons	4
05394	LED-12-SCBAY-W	12VAC/DC	S-8	BA15s	White	SC Bayonet Base 12V S8 Lamps	5
02687	LED-14-BA9S-G	14VAC/DC	T-3¼	BA9s	Green	756, 1813, 1815, 1816, 1889, 1891, 1892, 1893	1
02688	LED-14-BA9S-R	14VAC/DC	T-3¼	BA9s	Red	756, 1813, 1815, 1816, 1889, 1891, 1892, 1893	1
02689	LED-14-BA9S-W	14VAC/DC	T-3¼	BA9s	White	756, 1813, 1815, 1816, 1889, 1891, 1892, 1893	1
02691	LED-14-T1.75 Wedge-W	14VAC/DC	T-3¼	W2.1x4.6d	White	18, 37, 70, 73, 74	6
00345	LED-194-W	14VAC/DC	T-3¼	W2.1x9.5d	White	T3-1/4 Min Wedge Based Lamps 12/14V	7
02693	LED-24-BA9S-G	24-28VAC/DC	T-3¼	BA9s	Green	24MB, 28MB, 313, 757, 1818, 1819, 1820, 1829, 1843, 1864, 1873	1
02694	LED-24-BA9S-R	24-28VAC/DC	T-3¼	BA9s	Red	24MB, 28MB, 313, 757, 1818, 1819, 1820, 1829, 1843, 1864, 1873	1
02695	LED-24-BA9S-W	24-28VAC/DC	T-3¼	BA9s	White	24MB, 28MB, 313, 757, 1818, 1819, 1820, 1843, 1829, 1864, 1873	1
02696	LED-24-BA9S-Y	24-28VAC/DC	T-3¼	BA9s	Yellow	24MB, 28MB, 313, 757, 1818, 1819, 1820, 1843, 1829, 1864, 1873	1
05377	LED-24-Festoon-W	24VDC	Festoon 10mm	SV8.5mm	White	10 x 44 Xenon Festoons	4
02698	LED-24-MF-W	24-28VAC/DC	T-1¾	SX6s	White	327, 376, 385, 387, 7341	8
02702	LED-24-MG-W	24-28VAC/DC	T-1¾	S5.7s	White	276, 334, 388	9
02704	LED-24-PSB-G	24-28VAC/DC	T-2	TS5	Green	24PSB5, 28PSB5	2
02705	LED-24-PSB-R	24-28VAC/DC	T-2	TS5	Red	24PSB5, 28PSB5	2
02706	LED-24-PSB-W	24-28VAC/DC	T-2	TS5	White	24PSB5, 28PSB5	2
02707	LED-24-PSB-Y	24-28VAC/DC	T-2	TS5	Yellow	24PSB5, 28PSB5	2
02711	LED-24-T1.75 Wedge-W	24-28VAC/DC	T-1¾	W2.1x4.6d	White	17, 85	6
05742	LED-6-BA9S-W	6VAC/DC	T-3¼	BA9s	White	6MB, 44, 47, 238, 755, 1810, 1847, 1866	1



Guaranteed sale!

Move products out the door with Eiko's wire rack displays! Available in three recommended layouts and interchangeable header cards, you will have the option to pick and choose from our broad selection of LitespanLED® replacement lamps and fixtures – all guaranteed to facilitate sales!

LED Lamp and Fixture Merchandisers

Order Code	Item	Lamp Option	Fixture Option	Lamp & Fixture Option	Photo(s)
09895	LED9WA19/OMN/827-DIM-G8	2		2	 <p>Lamp Option</p>
09896	LED9WA19/OMN/830-DIM-G8	2		2	
09752	LED9WA19/OMN/840-DIM-G8	2		2	
09886	LED15WA19/OMN/827-DIM-G8	2			
09944	LED15WA19/OMN/830-DIM-G8	2			
09945	LED15WA19/OMN/840-DIM-G8	2			
08936	LED11WBR30/827K-DIM-G5	4		6	
08937	LED11WBR30/830K-DIM-G5	4		6	
08938	LED11WBR30/840K-DIM-G5	4		6	
09514	LED15WPAR38/FL/830-DIM-G7	4			
09477	LED12WPAR30S/FL/830-DIM-G7	4		2	
09156	LED11WPAR30/FL/830K-DIM-G6	4			
09185	LED7WPAR20/FL/830K-DIM-G6	8			
09374	LED27WPT40KMED-G7	4		4	
09387	LED54WPT40KMOG-G7	4		4	
09383	LED45WPT40KMOG-G7	4			
09878	LED5WB11E26/FIL/827-DIM-G7	12			
08732	LED5WB11/E26/830-DIM-G5	12			
08729	LED5WB11/E12/827-DIM-G5	12			
08730	LED5WB11/E12/830-DIM-G5	12			
09678	LED-DK4-9W930-DIM-G7	8			
09679	LED-DK4-9W940-DIM-G7	8			
09686	LED-DK6-15W930-DIM-G7	8			
09687	LED-DK6-15W940-DIM-G7	8			
09682	LED-DK6-11W930-DIM-G7	12			
09683	LED-DK6-11W940-DIM-G7	12			
09574	WMG-1C-50K-U		6	4	 <p>Lamp & Fixture Option</p>
09575	WMG-2C-50K-U		6		
09579	DTD-2C-50K-U		6	4	
09956	SCRG-50/D0/850-DIM-U-W		4		
09580	WMC-2C-50K-U		2		
09613	FLJ-3C-30K-Y-U		4		

EiKO USA: Terms, Conditions, & Shipping Procedures

Effective: January 15, 2018.

Supersedes all past terms and conditions of Price books and Sales Supplements.

Prices: As Shown and subject to change without notice.

Distributor Status: Distributors must purchase a minimum of \$3,500 annually in order to maintain distributor status.

Small Order Charge: Orders under \$250 will be assessed a \$15 small order charge (SOC).

Payment Terms: Net 30 days, from date of shipment as it appears on invoice. Postmark date on envelope will determine if payment has been made within terms. All orders received are subject to review and approval by our credit department. Orders received from customers with delinquent accounts may be subject to shipping delays, so please keep your account current.

Freight: NOTE: SoLux and EiKO products may be combined to meet prepaid freight requirements. EiKO Global, LLC will select the carrier of its choice.

1. All orders of \$1,000 or more will be shipped FREE FREIGHT F.O.B. destination via regular ground UPS, FedEx or USPS within the continental United States. Orders less than \$1,000 will be shipped F.O.B. origin.
2. UPS Second Day Air Blue – At the request of the distributor, orders will be billed at the UPS Second Day Air Rate.
3. UPS Next Day Air Red Label – At the request of the distributors, orders will be billed at the UPS Red Label Air rate.
4. Shipments made at the choice of the distributors, other than above, will be shipped F.O.B. shipping point.
5. Additional charges will apply for residential delivery.
6. Alaska, Hawaii and Puerto Rico – Orders of \$1,000 or more will be shipped free freight F.O.B. to a freight forwarder.
7. EiKO will no longer ship freight collect using the customer's account number.

We will cover the above items under normal Continental United States Policy. Therefore, you can achieve free freight to a border destination and then pick up the expense of forwarding the freight to your destination in Alaska, Hawaii or Puerto Rico. As an example, if you are a customer in Hawaii, you can have the goods for orders over \$1,000 shipped free freight to a freight forwarder. It would then be your responsibility to cover the freight to Hawaii.

Return Authorization:

1. You must contact EiKO Global, LLC for authorization to return defective products and shipment errors.
2. Return authorization will not be issued unless the distributor provides a valid invoice number showing when goods were purchased. A copy of this invoice must be included with the return.
3. Goods must be less than one year old to be eligible for return.
4. Where the request for return is neither defective merchandise nor error made by EiKO Global, LLC, the following policy will apply: A restocking charge of 20% will be charged on all authorized and acceptable goods. If goods are not returned in resalable condition they will be returned to the sender at the expense of the sender and no credit will be issued.

NOTE: All returns must have a return number on the outside of the box or they will be refused.

Shipment Discrepancies: All shipment discrepancies, damage, etc, must be reported within 10 days of the shipment date shown on the invoice.

General: We reserve the right to, at any time and without notice, discontinue or substitute brands.

Minimum Order Requirements for Linear Fluorescent Lamps: In order to avoid breakage, the minimum order quantity for T8 & T12 linear fluorescent lamps four feet or longer is 360. The minimum order quantity for programmed start T5 linear fluorescent lamps is 100. Mixing SKUs to meet the minimum order is allowed. Orders under \$1,000 will be charged \$70 LTL freight.

***Important Note About Minimum Advertised Pricing (MAPP):** In order to avoid predatory pricing and to maintain the integrity of the products, SoLux products purchased through EiKO Global, LLC may not be advertised for sale (Internet, electronic, print media, mailings or otherwise) by you, a sub-distributor or any other agent, below the minimum advertised price established in the current Distributor Net Price Schedule. This minimum advertised price will be known as and referred to as the MAPP price. Failure to comply with MAPP pricing requirements will result in the loss of your access to SoLux products.

EiKO Global, LLC: 23220 W. 84th St, Shawnee, KS 66227 • Ph: 1.800.852.2217 • F: 1.913.441.6679 • email: eiko@eiko.com

eiko.com

EiKO Canada: Terms, Conditions, & Shipping Procedures

Effective: July 1, 2017.

Supersedes all previously issued copies.

Ordering: All orders should be emailed to orderdesk@eiko.com or faxed to EiKO at 1-888-705-1335.

All orders received are subject to review and approval by our credit department.

Distributor Status: Distributors must purchase a minimum of \$1500.00 annually to maintain distributor status.

Prices: All prices are payable in Canadian funds. Prices are subject to change without notice and do not include applicable taxes. Any applicable taxes will be added to the invoice.

Minimum Order: \$75.00 minimum order requirement.

Payment Terms: Net 30 Days, from date of shipment as it appears on the invoice. Postmark date on envelope will determine if payment has been made within terms. All payments must be made in Canadian funds and mailed to below. EFT is available upon request.

EiKO Global, LLC (Canada)

81 King Street

Barrie, Ontario, L4N 6B5

Freight Terms: All pre-paid orders will be shipped F.O.B. destination via ground service and the carrier will be determined by Eiko Canada Ltd. Orders that do not meet the pre-paid amount will be shipped at customer's expense. At the request and expense of customer, orders can be shipped via air service. At the request of customer, orders can be drop shipped and pre-paid amounts will apply to shipping destination.

F.O.B Barrie, pre-paid as follows (before taxes):

British Columbia \$1,000.00	New Brunswick \$1,000.00
Alberta \$1,000.00	Nova Scotia \$1,000.00
Saskatchewan \$1,000.00	Prince Edward Island \$1,000.00
Manitoba \$750.00	Newfoundland and Labrador \$1,500.00
Ontario \$500.00	Yukon \$1,500.00
Montreal (Metropolitan Area) \$500.00	Northwest Territories \$1,500.00
All other points in Quebec \$750.00	Nunavut \$1,500.00

NOTE: - Pre-paid freight is \$1,000.00 in Ontario, Quebec and Manitoba when ordering Fluorescent or LED tubes 4 feet or longer.
- Expedited ground freight is available upon request for Western Canada. Pre-paid freight is \$1500.00.

Shipment Discrepancies/Damages: EiKO will credit or replace product found to arrive in damaged or broken condition on all pre-paid freight orders. All shipment discrepancies, damage, etc., must be reported within 10 days of the shipment date shown on the invoice.

Return Authorizations: You must contact EiKO within 90 days of delivery for a Return Authorization number. An RA number will only be provided if the customer has a valid invoice showing when the goods were purchased from EiKO. Goods must be less than one year old to be eligible for return. All returns must be shipped pre-paid with a copy of the invoice and RA included. A restocking charge of 25% will be charged on all authorized and acceptable goods. An order of 2 times the return value will be accepted as an offset to the restocking charge. Goods returned not in original packaging and not in resalable condition will be returned to sender, at the expense of the sender, and no credit will be issued.

General: EiKO reserves the right to discontinue and substitute brands at any time without notice.

EiKO Global Canada, LLC: 81 King St, Barrie, ON L4N 6B5 • Ph: 1.705.721.5189 • F: 1.705.721.7855 • Email: orderdesk@eiko.com

eiko.com

General Lighting Limited Warranty

EiKO brand lamps are warranted to be free of defective materials and workmanship for the period listed below. EiKO will replace or credit the distributor only for the cost of any lamp that fails under normal operating conditions and the use and operation conditions below due to defective materials or workmanship.

This warranty is limited to the replacement or credit of the lamp itself. This is buyer's exclusive remedy. Any other warranty, express or implied, including any warranty of merchantability or fitness for a particular purpose, is excluded and disclaimed. EiKO shall not be liable for any special, incidental or consequential damage including labor, loss of use, lost profits or injury to persons or property.

EiKO reserves the right to examine all lamps prior to the determination of warranty status. All lamps must be retained for warranty claims. The warranty period starts on the date of installation. If the date of installation is unknown or undetermined the warranty period will start at the wholesale purchase date.

Lamp Category	Warranty Period
LitespanLED® Line	60 months
Advantage™ Line	36 months
Metal Halide, High-Pressure Sodium, Mercury Vapor	15 months
Compact Fluorescent	12 months
Self Ballasted Compact Fluorescent	12 months
Linear Fluorescent (below 14 watt)	12 months
Linear Fluorescent (14 watt and above)	24 months
LCD	120 days

Credit is calculated as follows:

Credit (\$) = Invoiced Purchase Price (\$) x Unexpired Original Warranty Period (months)/Warranty Period

Use and Operating Conditions: Lamps must be used in UL approved fixtures with UL approved ballasts and installed according to local and national codes and standards. Use of occupancy sensors, dimmers or programmable systems with the lamp may void the warranty.

HID Lamps: Warranty is based on 5,000 hours per year maximum operation with a minimum of 8 hours operation per cycle. More frequent cycles will shorten lamp life and may not be covered under this warranty.


Fluorescent Lamps: Warranty is based on 4,000 hours per year maximum operation with a minimum of 3 hours operation per cycle. More frequent cycles will shorten lamp life and may not be covered under this warranty.

Large Lamps: Warranty is in effect for sales and installations on and after January 1, 2006.

LED: Warranty is in effect for sales and installations on and after July 1, 2010.

LCD: Warranty is in effect for sales and installations on and after July 1, 2009.

eiko.com



watch > like > follow >   



23220 W. 84th St, Shawnee, KS 66227 · (P) 1.800.852.2217 · (F) 1.800.492.8975
Canada: 81 King St, Barrie, ON L4N 6B5 · (P) 1.888.410.8151 · (F) 1.888.705.1335