


natural^{led}




LIGHTFAIR

INTERNATIONAL

The future. Illuminated.


2017



Product Catalog



▶▶▶ LED Lamps
& Fixtures



Version I
(LFI special)

Booth #101



Turning Light to Savings

naturalLED brings you the finest innovation in LED products for your residential and commercial projects. We provide a complete line of indoor and outdoor solutions.

Perfectly designed for residential, retail, commercial, and industrial applications.

Table of Contents

LIGHTFAIR 2107 PRODUCTS..... i - xviii

▶▶▶ Lamps & Tubes Page

Candelabra / Globe.....	01
R / BR - 900 series.....	01
A19 / A21.....	02
MR16.....	03
PAR Energy Star Rated - 800 series.....	03
PAR Energy Star Rated - 900 series.....	04
PAR Energy Star Rated.....	04
Bi-Pin.....	05
CornLight Retrofit.....	05
PL Plug-in.....	06
4W LED.....	06
Instant Fit Tube T5/T8.....	07
Integrated Driver Tube T5/T8.....	08

▶▶▶ Accessories Page

Recess Can Retrofit Accessories.....	31
Shoebox/ Area Light Accessories.....	31
Photocells.....	32
Sensors.....	32
Slim Wallpack Accessories.....	33
TWP Shield.....	33
Sensor for Highbay.....	34
Linear Highbay Accessories.....	34
Switch/ Pull Chain.....	35

▶▶▶ Fixtures

Page

Recess Can Retrofit- Energy Star Rated.....	11
Flush Mount - FMC Compact.....	12
Flush Mount - FMR Round.....	13
Flush Mount - FMS Streamlined.....	13
Flush Mount - FMM Modern.....	14
Flush Mount - Decorative Accent Light.....	14
Utility Wrap.....	15
Troffer.....	15
Troffer - DLC Premium.....	16
Linear - Low Bay / High Bay.....	16
Low Bay / High Bay.....	17
IP67 High Bay.....	17
IP65 Vapor Tight.....	18
Bulkhead Wall Light.....	18
Security Floodlight.....	19
Direct / Indirect - Decorative Wall Sconce.....	19
Security Lights.....	20
Canopy & Parking Garage.....	20
Slimline Canopy / Garage.....	21
Gas Station Canopy.....	22
WallPack - TWP Forward Throw.....	22
WallPack - Forward Throw / DLC Premium.....	23
WallPack - CWP Full Cutoff.....	23
WallPack - SWP Slim Wall Pack.....	24
Shoebox/Area Light.....	25
IP65 Floodlight.....	26

SLIM AREA LIGHT

29W / 50W / 75W / 100W / 180W / 240W / 360W



SAL series are low profile replacements for up to 1,250 watt traditional area lighting. Our fixtures are DLC 4.1 Premium with L90 rated chip and IP65 rated.

Four installation methods:

Swivel Bracket, Slip Fitter, EA6 Arm, Yoke Mount, Twin Up/Down Pendant

Lighting Distribution Type: 3 & 5



Dark Bronze



White

TYPE 3

SKU Code	Product Code	Watts	Lumens	Color Temp
7616	LED-FXSAL29/40K/DB/3S	29W	3,190	4000K
7617	LED-FXSAL29/50K/DB/3S	29W	3,190	5000K
7618	LED-FXSAL29/40K/WH/3S	29W	3,190	4000K
7619	LED-FXSAL29/50K/WH/3S	29W	3,190	5000K
7620	LED-FXSAL50/40K/DB/3S	50W	5,750	4000K
7621	LED-FXSAL50/50K/DB/3S	50W	5,750	5000K
7622	LED-FXSAL50/40K/WH/3S	50W	5,750	4000K
7623	LED-FXSAL50/50K/WH/3S	50W	5,750	5000K
7624	LED-FXSAL75/40K/DB/3S	75W	8,625	4000K
7625	LED-FXSAL75/50K/DB/3S	75W	8,625	5000K
7626	LED-FXSAL75/40K/WH/3S	75W	8,625	4000K
7627	LED-FXSAL75/50K/WH/3S	75W	8,625	5000K
7628	LED-FXSAL100/40K/DB/3S	100W	12,000	4000K
7629	LED-FXSAL100/50K/DB/3S	100W	12,000	5000K
7630	LED-FXSAL100/40K/WH/3S	100W	12,000	4000K
7631	LED-FXSAL100/50K/WH/3S	100W	12,000	5000K
7632	LED-FXSAL180/40K/DB/3S	180W	21,600	4000K
7633	LED-FXSAL180/50K/DB/3S	180W	21,600	5000K
7634	LED-FXSAL180/40K/WH/3S	180W	21,600	4000K
7635	LED-FXSAL180/50K/WH/3S	180W	21,600	5000K
7636	LED-FXSAL240/40K/DB/3S	240W	28,800	4000K
7637	LED-FXSAL240/50K/DB/3S	240W	28,800	5000K
7638	LED-FXSAL240/40K/WH/3S	240W	28,800	4000K
7639	LED-FXSAL240/50K/WH/3S	240W	28,800	5000K
7640	LED-FXSAL360/40K/DB/3S	360W	43,200	4000K
7641	LED-FXSAL360/50K/DB/3S	360W	43,200	5000K
7642	LED-FXSAL360/40K/WH/3S	360W	43,200	4000K
7643	LED-FXSAL360/50K/WH/3S	360W	43,200	5000K

TYPE 5

SKU Code	Product Code	Watts	Lumens	Color Temp
7644	LED-FXSAL29/40K/DB/5S	29W	3,190	4000K
7645	LED-FXSAL29/50K/DB/5S	29W	3,190	5000K
7646	LED-FXSAL29/40K/WH/5S	29W	3,190	4000K
7647	LED-FXSAL29/50K/WH/5S	29W	3,190	5000K
7648	LED-FXSAL50/40K/DB/5S	50W	5,750	4000K
7649	LED-FXSAL50/50K/DB/5S	50W	5,750	5000K
7650	LED-FXSAL50/40K/WH/5S	50W	5,750	4000K
7651	LED-FXSAL50/50K/WH/5S	50W	5,750	5000K
7652	LED-FXSAL75/40K/DB/5S	75W	8,625	4000K
7653	LED-FXSAL75/50K/DB/5S	75W	8,625	5000K
7654	LED-FXSAL75/40K/WH/5S	75W	8,625	4000K
7655	LED-FXSAL75/50K/WH/5S	75W	8,625	5000K
7656	LED-FXSAL100/40K/DB/5S	100W	12,000	4000K
7657	LED-FXSAL100/50K/DB/5S	100W	12,000	5000K
7658	LED-FXSAL100/40K/WH/5S	100W	12,000	4000K
7659	LED-FXSAL100/50K/WH/5S	100W	12,000	5000K
7660	LED-FXSAL180/40K/DB/5S	180W	21,600	4000K
7661	LED-FXSAL180/50K/DB/5S	180W	21,600	5000K
7662	LED-FXSAL180/40K/WH/5S	180W	21,600	4000K
7663	LED-FXSAL180/50K/WH/5S	180W	21,600	5000K
7664	LED-FXSAL240/40K/DB/5S	240W	28,800	4000K
7665	LED-FXSAL240/50K/DB/5S	240W	28,800	5000K
7666	LED-FXSAL240/40K/WH/5S	240W	28,800	4000K
7667	LED-FXSAL240/50K/WH/5S	240W	28,800	5000K
7668	LED-FXSAL360/40K/DB/5S	360W	43,200	4000K
7691	LED-FXSAL360/50K/DB/5S	360W	43,200	5000K
7670	LED-FXSAL360/40K/WH/5S	360W	43,200	4000K
7671	LED-FXSAL360/50K/WH/5S	360W	43,200	5000K

Mounting

SKU Code	Product Code	Description
P10101	MT-SAL/SF/DB	Slip Fitter Mount for SAL Dark Bronze
P10102	MT-SAL/SF/WH	Slip Fitter Mount for SAL White
P10103	MT-SAL/SB/DB	Swivel Bracket Mount for SAL Dark Bronze
P10104	MT-SAL/SB/WH	Swivel Bracket Mount for SAL White
P10105	MT-SAL/EA6/DB	6" Inch Extruded Arm for SAL Dark Bronze
P10106	MT-SAL/EA6/WH	6" Inch Extruded Arm for SAL White
P10107	MT-SAL/DPB/DB	Dual Pendant Box 3/4" NPT Dark Bronze
P10108	MT-SAL/DPB/WH	Dual Pendant Box 3/4" NPT White
P10111	MT-SAL/YK9/DB	9" Yoke Mount for SAL (29-100W) Dk Bronze
P10112	MT-SAL/YK9/WH	9" Yoke Mount for SAL (29-100W) White
P10113	MT-SAL/YK15/DB	15" Yoke Mount for SAL 180-360W) Dk Bronze
P10114	MT-SAL/YK15/WH	15" Yoke Mount for Slim Area Light (180-360W)

LINEAR HIGHBAY



LHB series, our new design captures all of the beneficial characteristics of LED light and optimizes the benefits to create a high performance fixture that will endure many years of service without becoming obsolete.

These linear high bays are DLC 4.1 Premium with L90 rated chip, extremely durable, yet light weight. Our fixtures are available in a wide range of wattages, delivering up to 39,000 lumens of consistent light and color.



Easy knockout for motion sensor



Optional PIR Occupancy Sensor with interchangeable lens (Aisle & Area)



Chain Hung (chain and safety hooks included with all fixtures)

3 mounting options



Pendant Mount Option
*Pendant not included



Emergency Battery Back Up Available



Yoke/Surface Mount Option

SKU Code	Product Code	Watts	Lumens	Color Temp
7406	LED-FXHBL75/22FR/840	75W	9,750	4000K
7407	LED-FXHBL75/22FR/850	75W	9,750	5000K
7408	LED-FXHBL100/22FR/840	100W	13,000	4000K
7409	LED-FXHBL100/22FR/850	100W	13,000	5000K
7410	LED-FXHBL150/22FR/840	150W	19,500	4000K
7411	LED-FXHBL150/22FR/850	150W	19,500	5000K
7442	LED-FXHBL160/22FR/840	160W	16,800	4000K
7443	LED-FXHBL160/22FR/850	160W	16,800	5000K
7412	LED-FXHBL210/44FR/840	210W	27,300	4000K
7413	LED-FXHBL210/44FR/850	210W	27,300	5000K
7417	LED-FXHBL300/44FR/850	300W	39,472	4000K
7488	LED-FXHBL150/22FR/850/480	150W	19,475	5000K
7486	LED-FXHBL300/44FR/850/480	300W	39,472	5000K

HIGHBAY

Pendant, Hook or
Surface Mountable

► **Round Highbay**

Wattage: 150W

Lumens: 16,500



IP65
outdoor rated

► **IP65 Linear HighBay**

Wattage: 150W

Lumens: 19,500



LINEAR LIGHTING

Shop Light / Strip



SKU Code	Product Code	Watts	Lumens	Color Temp
7593	LED-FXUSL40/48FR/840/MV	40W	4,000	4000K
7594	LED-FXUSL40/48FR/850/MV	40W	4,000	5000K
7602	LED-FXUSL40/48FR/840/347	40W	4,000	4000K
7603	LED-FXUSL40/48FR/850/347	40W	4,000	5000K

Utility Wrap



SKU Code	Product Code	Watts	Lumens	Color Temp
7074	LED-FXUWS29/40K	29W	3,220	4000K
7075	LED-FXUWS29/50K	29W	3,220	5000K

Vapor Tight

for parking garage



SKU Code	Product Code	Watts	Lumens	Color Temp
7448	LED-FXVTL29/40K	29W	3,238	4000K
7449	LED-FXVTL29/50K	29W	3,434	5000K
7450	LED-FXVTL58/40K	58W	6,424	4000K
7451	LED-FXVTL58/50K	58W	7,010	5000K

Motion Sensors

7582	LED-FXVTL29/40K-SEN	29W	3,238	4000K
7583	LED-FXVTL29/50K-SEN	29W	3,434	5000K
7584	LED-FXVTL58/40K-SEN	58W	6,424	4000K
7585	LED-FXVTL58/50K-SEN	58W	7,010	5000K

Tubes



SKU Code	Product Code	Watts	Lumens	Color Temp
----------	--------------	-------	--------	------------

Instant Fit

5992	LED28T5/FR35/840/IF	28W	3,500	4000K
5993	LED28T5/FR35/850/IF	28W	3,500	5000K
5990	LED14T8/FR18/840/IF	14W	1,800	4000K
5991	LED14T8/FR18/850/IF	14W	1,800	5000K

Integrated Tube

5955	LED15T8/FR18/840 (Bypass)	15W	1,800	4000K
5956	LED15T8/FR18/850 (Bypass)	15W	1,800	5000K



HO (R17d) Base

Single Pin Base



Our Instant-Fit T5/T8 and 8-ft T8 LED HO & Single Pin Base fits your existing fluorescent system and utilizes the existing electrical T5/T8 fluorescent ballast without re-wiring.

INDOOR LIGHTING

► Flush Mount Modern

16-inch
120V

Wattage: 18W / 22W / 26W
Lumens: 1,380 / 1,652 / 1,960

Our design features a low-profile body with nickel finish accents and a white acrylic diffuser.



14-inch / 12-inch
120V

277V



► Flush Mount Streamlined

Wattage: 14W / 22W
Lumens: 980 / 1,540

Simple and Sleek design with even light distribution. 11-inch and 15-inch.





► **Flush Mount Round**

Easy Installation

Retrofit for CFL & Incandescent Flush Mount



Wattage: 12W / 14W / 22W
Lumens: 800 / 1,143 / 1,672

Our FMR provides energy savings with sleek and compact design for easy installation.

► **Decorative Accent**

RETROFIT / SAVE ENERGY
 Replace CFL and Incandescent with LED



Incandescent and CFL



Wattage: 23W
Lumens: 1,610 / 2,000
 Available in 12-inch and 24-inch

► **Under Cabinet Lights**

Wattage: 4W / 9W
Lumens: 280 / 490

Available in 9-inch and 18-inch with connector.

Quick Connector
 (Optional)



3 foot Power Cord
 and connector
 included



SECURITY LIGHTING

 FOR
WET Location



► **Security Lights**

Wattage: 20W
Lumens: 1,400

Ideal for security lighting solution:
Residential, Commercial and Retail.

motion sensor

► **Up/Down Sconce Light**

Wattage: 14W / 22W
Lumens: 980 / 1,540



Vertical Lighting suitable for
indoor and outdoor.





► **Cylinder**

Wattage: 17W / 23W / 30W
Lumens: 1,300 / 1,800 / 2,400
Surface Mount/ Wall Mount

► **Bulkhead**

Wattage: 10W
Lumens: 900 Lm

Available in Black and White



► **Jelly Jar**

Industrial Quality
Die-cast aluminum Jelly Jar 1,800 Lumens and only uses 20 Watts.
Wall / Ceiling and Pendant Mount Available.



OUTDOOR FIXTURE




50W / 120W / 200W / 300W

► HID to LED Retrofit

Wattage: 50W / 120W / 200W / 300W

Lumens: 5,000 / 12,000 / 20,000 / 30,000

High Quality LED Retrofit Kits with separate driver for HID equivalent solutions. Multiple mounting options and adjust-ability for Indoor and outdoor applications to fit various fixture types. Shoebox, High Bay, Low Bay, Flood, Wall Pack and many more. Provides many years of energy saving service.



► Traditional Wall Pack

Wattage: 28W / 42W / 59W / 80W

Lumens: 3,000 / 4,886 / 7,199 / 10,416



Cast-aluminum housing with excellent thermal design. Delivering up to 10,000 lumens. Replaces metal halide luminaires and high pressure sodium, with energy saving up to 80%.



► **Slim Wall Pack**

Wattage: 15W / 29W / 50W
Lumens: 1,740 / 3,268 / 3,329

Excellent thermal design easy installation. Our slim wall pack has optional mounting available and a threaded knockout for a photo cell if needed.



3/4" NPT
Knuckle Mount



Swivel Bracket



Slip Fitter



Button Photocell
(120-277V)

► **3 Color Choices**



Bronze Black White



Optional
Microwave
Motion
Sensor

Optional:
New Drop Lens

HIGH EFFICACY



► **Slim Canopy**

Wattage: 28W / 42W / 59W / 70W
Lumens: 3,236 / 4,871 / 6,800 / 5,900

Our Slim canopy is DLC V4.1 Premium listed with L90 Rated Chip, and UL listed for wet locations with an IP65 rating.

Troffer



Emergency
Battery Back Up
Available

2'x2' / 2'x4'

► Troffer

Wattage: 20W / 30W / 49W

Lumens: 2,600 / 3,900 / 6,760

Our naturalLED Troffer is the perfect solution for your interior lighting needs. The troffers come in 2x2 and 2x4 for TBar/Grid ceilings and are designed for easy installation and maximum energy savings.

All troffers are DLC 4.1 Premium with L90 rated chip and deliver up to 6,900 lumens with excellent consistent color.



Gas Station Canopy



► Gas Station Canopy

Wattage: 45W / 75W / 100W / 150W

Lumens: 5,400 / 9,000 / 12,000 / 18,052

Gas Station Canopy (GSC) is designed to replace metal halide light fixtures in gas station canopies easily and cost effectively. Our gas station is DLC 4.1 Premium with L90 rated chip.

► 45W / 75W



► 100W / 150W

IP65
outdoor rated



LAMPS

IP65
outdoor rated

DLC
QUALITY



► Corn Light Retrofit for HID

Wattage: 20W~100W

Lumens: 2,200~13,000

naturaLED® LED Corn Light features high lumen output and is omni directional. Perfect for industrial, commercial and residential applications.

Available in E39 and E26 base.



► A19 GU24

Wattage: 9W

Lumens: 800

Omni-directional lamp.
Rated for enclosed fixture.

Item # 5923



► A19 E26

Wattage: 12W

Lumens: 1,100

Omni-directional lamp

Item # 5860



CRI
90



► **PAR Series**

Wattage: 8W / 10W / 15W

Lumens: 500 / 800 / 1,200

Complete line of PAR Series range
from PAR 20 to PAR 38.



► **BR30 CRI90**

Wattage: 12W

Lumens: 900

CRI 90

Item # 5842



CRI
90

Color Rendering Index (CRI) describes how an object appears to the human eye based on ideal or natural light source. CRI are mainly used in lighting to compare how "true" and "natural" objects are rendered. The value 100 means that there is no difference in color rendition between the light of the observed light bulb and the light of the reference illuminant., lighting with a CRI of 85 to 90 is typically "excellent" at rendering colors of objects while CRI90 or greater are "superior".



LAMPS



↑ INSTANT FIT

PLUG-IN
4-pin base

▶ **PL Vertical**


*Wattage: 7W / 9W
Lumens: 700 / 900*

Our energy efficient PL LED 4-Pin Instant Fit, multi-watt lamp operates with a compact fluorescent electronic ballast. This lamp is a direct replacement for a 18W, or 26W 4-Pin PL/ CFL lamp.


▶ **PL Horizontal**

*Wattage: 7W / 9W
Lumens: 700 / 900*

Instant Fit (works with existing electronic ballast), direct replacement for CFL: 18 Watt, and 26 Watt. Fits Vertically or Horizontally with rotatable G24 base. The lamps wattage input and lumen output is determined by the existing electronic PL/CFL ballast.



**Rotatable
G24 base**





► **MR16 GU10**

*Wattage: 7W
Lumens: 500*

Dimmable 3000K and 5000K
consistent color.

Item #5938 / #5939




► **Candelabra**

*Wattage: 4.5W
Lumens: 300*



LAMPS



Turning Light into Savings ▶▶▶

01

Candelabra / Globe



SKU Code	Product Code	Watts	Watt Equiv.	Color Temp
5837	LED5CAB/32L/E12/27K	5W	40W	2700K
5838	LED5CAB/32L/E12/30K	5W	40W	3000K
5839	LED5CAB/32L/E12/50K	5W	40W	5000K
5814	LED6G25/45L/27K	6W	40W	2700K
5723	LHO8G25/DIM/30K	8W	50W	3000K



02

R / BR
900 Series

SKU Code	Product Code	Watts	Watt Equiv.	Color Temp
5834	LED8R20/50L/927	8W	50W	2700K
5982	LED8R20/52L/950	8W	50W	5000K
5835	LED9BR30/65L/927	9W	65W	2700K
5983	LED9BR30/71L/950	9W	65W	5000K
5987	LED11BR30/80L/830	11W	70W	3000K
5842	LED12BR30/90L/927	12W	75W	2700K
5978	LED12BR30/90L/940	12W	75W	4000K
5984	LED12BR30/95L/950	12W	75W	5000K
5894	LED12BR30/80L/927	12W	65W	2700K
5986	LED14BR40/100L/930	14W	90W	3000K
5836	LED15BR40/120L/927	15W	90W	2700K
5985	LED15BR40/130L/950	15W	90W	5000K
5896	LED14BR40/100L/927	14W	75W	2700K



03

R / BR
800 Series

SKU Code	Product Code	Watts	Watt Equiv.	Color Temp
5783	LED11BR30/85L/27K	11W	65W	2700K
5841	LED11BR30/85L/50K	11W	65W	5000K
5886	LED8BR30/65L/827CP (2-pack)	8W	50W	2700K
5895	LED12BR40/105L/27	12W	75W	2700K
5816	LED13BR40/105L/27K	13W	70W	2700K
5784	LED17BR40/140L/27K	17W	100W	2700K
5707	LHO13R40/DIM/30K	13W	80W	3000K
5724	LHO18R40/DIM/30K	18W	120W	3000K



04

A19 / A21



SKU Code	Product Code	Watts	Watt Equiv.	Color Temp
5946	LED6A19/48L/827	6W	40W	2700K
5919	LED6A19/48L/830	6W	40W	3000K
5947	LED6A19/48L/840	6W	40W	4000K
5948	LED6A19/48L/850	6W	40W	5000K
5920	LED9A19/80L/827	9W	60W	2700K
5976	LED9A19/80L/830	9W	60W	3000K
5921	LED9A19/80L/840	9W	60W	4000K
5922	LED9A19/80L/850	9W	60W	5000K
5859	LED10A19/80L/927	10W	60W	2700K
5860	LED12A19/110L/827	12W	100W	2700K
5977	LED12A19/110L/830	12W	100W	3000K
5831	LED12A19/110L/840	12W	100W	4000K
5832	LED12A19/110L/850	12W	100W	5000K
5808	LED6A19/50L/50K	6.8W	40W	5000K
5822	LED9.5A19/87L/40K	9.5W	60W	4000K
5881	LED9.5A19/81L/827/CP (2-pack)	9.5W	60W	2700K
5918	LED9A19/EC/80L/GU24/827	9W	60W	2700K
5980	LED9A19/EC/80L/827	9W	60W	2700K
5957	LED15A21/160L/827	15W	150W	2700K
5962	LED15A21/160L/830	15W	150W	3000K
5963	LED15A21/160L/840	15W	150W	4000K
5964	LED15A21/160L/850	15W	150W	5000K



05

MR16



SKU Code	Product Code	Watts	Watt Equiv.	Color Temp
* 5802	LED7MR16/40L/FL/30K	7W	35W	3000K
5864	LHO-7MR16/FL/30K	7W	50W	3000K
5849	LHO-7MR16/FL/50K	7W	50W	5000K
* 5801	LED7MR16/45L/GU10/FL/30K	7W	50W	3000K
* 5821	LED7MR16/45L/GU10/FL/50K	7W	50W	5000K
* 5678	LHO-4MR11/NFL/50K (12V)	4W	25W	5000K

*Non Dimmable



06

PAR Energy Star Rated
800 Series

SKU Code	Product Code	Watts	Watt Equiv.	Color Temp
5855	LED7.6PAR20/50L/FL/830	7.6W	50W	3000K
5856	LED7.6PAR20/50L/FL/840	7.6W	50W	4000K
5857	LED7.6PAR20/50L/FL/850	7.6W	50W	5000K
5862	LED9PAR30/80L/FL/840	9W	60W	4000K
5863	LED9PAR30/80L/FL/850	9W	60W	5000K
5868	LED9PAR30L/80L/FL/840	9W	60W	4000K
5869	LED9PAR30L/80L/FL/850	9W	60W	5000K
5885	LHO13PAR30L/100L/FL/30K/277	13W	65W	3000K
* 5873	LED14.5PAR38/OD/120L/FL/830	14.5W	100W	3000K
* 5874	LED14.5PAR38/OD/120L/FL/840	14.5W	100W	4000K

*Outdoor Rated



07

PAR Energy Star Rated
900 Series

SKU Code	Product Code	Watts	Watt Equiv.	Color Temp
5924	LED8PAR20/50L/FL/930	8W	50W	3000K
5925	LED8PAR20/50L/FL/950	8W	50W	5000K
5926	LED10PAR30/80L/FL/930	10W	75W	3000K
5927	LED10PAR30/80L/FL/950	10W	75W	5000K
* 5928	LED10PAR30L/OD/80L/FL/930	10W	75W	3000K
* 5929	LED10PAR30L/OD/80L/FL/950	10W	75W	5000K
* 5930	LED15PAR38/OD/120L/FL/930	15W	100W	3000K
* 5931	LED15PAR38/OD/120L/FL/950	15W	100W	5000K

*Outdoor Rated



08

PAR Lamps



SKU Code	Product Code	Watts	Watt Equiv.	Color Temp
5788	LHO-7.5PAR20/54L/FL/40K	7.5W	50W	4000K
5789	LHO-7.5PAR20/58L/FL/50K	7.5W	50W	5000K
5754	LED9.5PAR20/50L/NFL/30K	9.5W	50W	3000K
5755	LED9.5PAR20/50L/NFL/50K	9.5W	50W	5000K
5756	LED14PAR30/88L/NFL/30K	14W	75W	3000K
5764	LED14PAR30/80L/FL/30K	14W	75W	3000K
5757	LED14PAR30/90L/NFL/50K	14W	75W	5000K
5765	LED14PAR30/86L/FL/50K	14W	75W	5000K
5790	LHO-9.5PAR30L/75L/FL/30K	9.5W	75W	3000K
5791	LHO-9.5PAR30L/75L/FL/40K	9.5W	75W	4000K
5792	LHO-9.5PAR30L/83L/FL/50K	9.5W	75W	5000K
5758	LED14PAR30L/90L/NFL/30K	14W	75W	3000K
5759	LED14PAR30L/90L/NFL/50K	14W	75W	5000K
5767	LED14PAR30L/86L/NFL/50K	14W	75W	5000K
5630	LED14PAR30L/DIM/NFL/40K	14W	75W	4000K
5654	LED14PAR30L/DIM/FL/40K	14W	75W	4000K
5793	LHO-13.5PAR38/107L/FL/30K	13.5W	85W	3000K
5794	LHO-13.5PAR38/107L/FL/40K	13.5W	85W	4000K
5632	LED17PAR38/DIM/NFL/30K	17W	85W	3000K



09

Bi-Pin
Low/Line Voltage

SKU Code	Product Code	Watts	Watt Equiv.	Color Temp
5828	LHO-JC1.6T4G4/30K	1.6W	-	3000K
5848	LHO-JC1.6T4G4/50K	1.6W	-	5000K
* 5826	LHO-JCD3T4G9/30K	3W	-	3000K
* 5830	LHO-JCD3T4G9/50K	3W	-	5000K

*Non Dimmable



10

HID Retrofit CornLight



SKU Code	Product Code	Watts	Watt Equiv.	Color Temp
5965	LED20HID/E26/220L/827	20W	70W	2700K
5966	LED20HID/E26/220L/850	20W	70W	5000K
5967	LED28HID/E26/310L/827	28W	100W	2700K
5968	LED28HID/E26/310L/850	28W	100W	5000K
5969	LED27HID/EX39/300L/830	26W	100W	3000K
5944	LED27HID/EX39/300L/850	26W	100W	5000K
5970	LED36HID/EX39/400L/830	35W	150W	3000K
5971	LED36HID/EX39/400L/850	35W	150W	5000K
5972	LED54HID/EX39/600L/840	52W	250W	4000K
5949	LED54HID/EX39/600L/850	52W	250W	5000K
5973	LED75HID/EX39/800L/840	75W	320W	4000K
5950	LED75HID/EX39/800L/850	75W	320W	5000K
5974	LED100HID/EX39/1300L/840	100W	400W	4000K
5975	LED100HID/EX39/1300L/850	100W	400W	5000K



11

PL Plug-in
Instant Fit (Multi-Watt)50,000
Rated
Life Hours

SKU Code	Product Code	Watts	Watt Equiv.	Color Temp
CRI 80				
4500	LED7PL/H/4P/835/IF	7W	18W	3500K
4501	LED7PL/H/4P/840/IF	7W	18W	4000K
4502	LED7PL/V/4P/835/IF	7W	18W	3500K
4503	LED7PL/V/4P/840/IF	7W	18W	4000K
4504	LED9PL/H/4P/835/IF	9W	26W	3500K
4505	LED9PL/H/4P/840/IF	9W	26W	4000K
4506	LED9PL/V/4P/835/IF	9W	26W	3500K
4507	LED9PL/V/4P/840/IF	9W	26W	4000K
CRI 90				
5932	LED9PL/H/4P/935/IF	5/7/9W	13/18/26W	3500K
5933	LED9PL/H/4P/940/IF	5/7/9W	13/18/26W	4000K
5934	LED9PL/V/4P/935/IF	5/7/9W	13/18/26W	3500K
5935	LED9PL/V/4P/940/IF	5/7/9W	13/18/26W	4000K



12

LED
4W30,000
Rated
Life Hours

SKU Code	Product Code	Watts	Watt Equiv.	Color Temp
5547	LHO-4G12/CDL	4W	140	6600K
5546	LHO-4G12/WW	4W	110	3300K
5557	LHO-4T9/CDL	4W	140	6600K
5556	LHO-4T9/WW	4W	110	3300K



13

Instant Fit Tube



SKU Code	Product Code	Watts	Watt Equiv.	Color Temp
----------	--------------	-------	-------------	------------

T5

5902	LED28T5/FR32/840/IF	28W	54W	4000K
5903	LED28T5/FR32/850/IF	28W	54W	5000K

T5 Dimmable

5992	LED28T5/FR35/840/IF	28W	54W	4000K
5993	LED28T5/FR35/850/IF	28W	54W	5000K

T8

5988	LED10T8/24FR10/840/IF	10W	17W	4000K
5989	LED10T8/24FR10/850/IF	10W	17W	5000K
5850	LED10T8/24FR11/835/IF	10W	17W	3500K
5851	LED10T8/24FR11/840/IF	10W	17W	4000K
5852	LED10T8/24FR11/850/IF	10W	17W	5000K
5891	LED11T8/36FR14/840/IF	11W	25W	4000K
5892	LED11T8/36FR14/850/IF	11W	25W	5000K
5990	LED14T8/FR18/840/IF	14W	28W	4000K
5991	LED14T8/FR18/850/IF	14W	28W	5000K
5914	LED15.5T8/FR18/840/IF	15.5W	32W	4000K
5915	LED15.5T8/FR18/850/IF	15.5W	32W	5000K
5844	LED17.5T8/FR19/835/IF	17W	32W	3500K
5845	LED17.5T8/FR19/840/IF	17W	32W	4000K
5846	LED17.5T8/FR19/850/IF	17W	32W	5000K
5916	LED18T8/FR22/840/IF	18W	32W	4000K
5917	LED18T8/FR22/850/IF	18W	32W	5000K

Single

5887	LED38T8/96FR44/840/IF	38W	75W	4000K
5888	LED38T8/96FR44/850/IF	38W	75W	5000K

R17d

5897	LED42T8/96FR50/R17d/840/IF	42W	110W	4000K
5898	LED42T8/96FR50/R17d/850/IF	42W	110W	5000K



14

Integrated Driver



SKU Code	Product Code	Watts	Watt Equiv.	Color Temp
5951	LED9T8/24FR10/840	9W	17W	4000K
5952	LED9T8/24FR10/850	9W	17W	5000K
5953	LED15T8/36FR16/840	15W	25W	4000K
5954	LED15T8/36FR16/850	15W	25W	5000K
5955	LED15T8/FR18/840	15W	32W	4000K
5956	LED15T8/FR18/850	15W	32W	5000K
5958	LED43T8/96FR55/840	43W	110W	4000K
5959	LED43T8/96FR55/850	43W	110W	5000K
5960	LED43T8/96FR55/R17D/840	43W	110W	4000K
5961	LED43T8/96FR55/R17D/850	43W	110W	5000K
* 5778	LED10T8/24FR10/840	10W	25W	4000K
* 5774	LED10T8/24FR10/850	10W	25W	5000K
* 5779	LED10T8/36FR10/840	10W	25W	4000K
* 5817	LED14T8/FR17/840	14W	32W	4000K
* 5818	LED14T8/FR17/850	14W	32W	5000K
* 5811	LED40T8/96FR43/840	40W	75W	4000K

* Plastic/ Aluminum Design



FIXTURES



Turning Light into Savings ▶▶▶

01

Retrofit Recess Can Energy Star Rated (CRI 80)



SKU Code	Product Code	Watts	Color Temp
7092	LED4RL-56L30K	9W	3000K
7172	LED4RL-56L40K	9W	4000K
7173	LED4RL-56L50K	9W	5000K
7562	LED4RL-65L830	9W	3000K
7566	LED4RL-65L840	9W	4000K
7567	LED4RL-65L850	9W	5000K
7198	LED4RL-56L827CP (2-pack)	9W	2700K
7093	LED4RL-56L830CP (2-pack)	9W	3000K
7174	LED6RL-88L40K	13W	4000K
7563	LED6RL-98L830	13W	3000K
7568	LED6RL-98L840	13W	4000K
7569	LED6RL-98L850	13W	5000K
7199	LED6RL-88L827CP (2-pack)	13W	2700K
7095	LED6RL-88L830CP (2-pack)	13W	3000K
7135	LED6RL-110L40K/MV	15W	4000K



02

Retrofit Recess Can Energy Star Rated (CRI 90)



SKU Code	Product Code	Watts	Color Temp
7580	LED4RL-58L927	9W	2700K
7578	LED4RL-58L930	9W	3000K
7581	LED6RL-88L927	13W	2700K
7579	LED6RL-88L930	13W	3000K



03

Flush Mount FMC Compact



SKU Code	Product Code	Watts	Color Temp
7055	LED7FMC-110L830	16W	3000K
7056	LED7FMC-110L840	16W	4000K
7057	LED7FMC-110L850	16W	5000K
7454	LED7FMC-70L830	10W	3000K
7455	LED7FMC-70L840	10W	4000K
7456	LED7FMC-70L850	10W	5000K



04

Flush Mount FMR Round



SKU Code	Product Code	Watts	Color Temp
7058	LED8FMR-80L830	12W	3000K
7059	LED8FMR-80L840	12W	4000K
7142	LED12FMR-110L830	14W	3000K
7143	LED12FMR-110L840	14W	4000K
7156	LED12FMR-110L850	14W	5000K
7146	LED16FMR-160L830	22W	3000K
7147	LED16FMR-160L840	22W	4000K
7157	LED16FMR-160L850	22W	5000K



05

Flush Mount FMS Streamlined



SKU Code	Product Code	Watts	Color Temp
7418	LED11FMS-98L830-BZ	14W	3000K
7419	LED11FMS-98L840-BZ	14W	4000K
7424	LED11FMS-98L830-NI	14W	3000K
7425	LED11FMS-98L840-NI	14W	4000K
7421	LED15FMS-154L830-BZ	22W	3000K
7422	LED15FMS-154L840-BZ	22W	4000K
7427	LED15FMS-154L830-NI	22W	3000K
7428	LED15FMS-154L840-NI	22W	4000K



06

Flush Mount FMM Modern



120V



277V



SKU Code	Product Code	Watts	Color Temp
120V			
7430	LED12FMM-138L/830-NI	18W	3000K
7431	LED12FMM-138L/840-NI	18W	4000K
7433	LED14FMM-165L/830-NI	22W	3000K
7434	LED14FMM-165L/840-NI	22W	4000K
7533	LED16FMM-196L/830-NI	26W	3000K
7534	LED16FMM-196L/840-NI	26W	4000K
277V			
7596	LED12FMM-138L840-NI/MV	18W	4000K
7597	LED14FMM-165L840-NI/MV	22W	4000K
7598	LED16FMM-196L840-NI/MV	26W	4000K



07

Flush Mount Decorative Accent Light



SKU Code	Product Code	Watts	Color Temp
7018	LED-FXDAL23/12FR/830/NI	23W	3000K
7019	LED-FXDAL23/12FR/840/NI	23W	4000K
7020	LED-FXDAL23/24FR/830/NI	23W	3000K
7021	LED-FXDAL23/24FR/840/NI	23W	4000K



08

Utility Wrap

50,000
Rated
Life Hours

SKU Code	Product Code	Watts	Color Temp
7074	LED-FXUWS29/40K	29W	4000K
7075	LED-FXUWS29/50K	29W	5000K



09

Flat Panel

Dimmable
0-10V50,000
Rated
Life Hours

SKU Code	Product Code	Watts	Color Temp
7100	LED-FXPNL25/2X2/840	25W	4000K
7101	LED-FXPNL32/1X4/840	32W	4000K
7102	LED-FXPNL40/2X4/840	40W	4000K

Surface Mount Kit

SKU Code	Product Code	Description
P10097	MT-2X2BOX	Surface Mount Kit for 2' x 2'
P10096	MT-1X4BOX	Surface Mount Kit for 1' x 4'
P10098	MT-2X4BOX	Surface Mount Kit for 2' x 4'
P10099	MT-PNL-HOOK-4PCS	Earthquake hook for 2' x 2' & 1' x 4'
P10100	MT-PNL-HOOK-6PCS	Earthquake hook for 2' x 4'



10

Troffer
DLC PremiumDimmable
0-10V50,000
Rated
Life Hours

SKU Code	Product Code	Watts	Color Temp
7034	LED-FXTF20/2X2/835	20W	3500K
7035	LED-FXTF20/2X2/840	20W	4000K
7036	LED-FXTF20/2X2/850	20W	5000K
7037	LED-FXTF30/2X4/835	30W	3500K
7038	LED-FXTF30/2X4/840	30W	4000K
7039	LED-FXTF30/2X4/850	30W	5000K
7040	LED-FXTF49/2X4/835	49W	3500K
7041	LED-FXTF49/2X4/840	49W	4000K
7042	LED-FXTF49/2X4/850	49W	5000K



11

Linear Low Bay / High Bay
DLC PremiumDimmable
0-10V50,000
Rated
Life Hours

SKU Code	Product Code	Watts	Color Temp
7406	LED-FXHBL75/22FR/840	75W	4000K
7407	LED-FXHBL75/22FR/850	75W	5000K
7408	LED-FXHBL100/22FR/840	100W	4000K
7409	LED-FXHBL100/22FR/850	100W	5000K
7410	LED-FXHBL150/22FR/840	150W	4000K
7411	LED-FXHBL150/22FR/850	150W	5000K
7442	LED-FXHBL160/22FR/840	160W	4000K
7443	LED-FXHBL160/22FR/850	160W	5000K
7412	LED-FXHBL210/44FR/840	210W	4000K
7413	LED-FXHBL210/44FR/850	210W	5000K
7416	LED-FXHBL300/44FR/840	300W	4000K
7417	LED-FXHBL300/44FR/850	300W	5000K
7488	LED-FXHBL150/22FR/850/480 (480V)	150W	5000K
7486	LED-FXHBL300/44FR/850/480 (480V)	300W	5000K



12

Low Bay / High Bay



SKU Code	Product Code	Watts	Color Temp
7125	LED-FXLB70/40K	70W	4000K
7126	LED-FXLB70/50K	70W	5000K
7128	LED-FXHB100/40K	100W	4000K
7129	LED-FXHB100/50K	100W	5000K
7131	LED-FXHB165/40K	165W	4000K
7132	LED-FXHB165/50K	165W	5000K
7170	LED-FXHB200/40K	200W	4000K
7171	LED-FXHB200/50K	200W	5000K
P10027	WG-CBL18/WH (Wire Guard)	-	-



13

IP67 High Bay



SKU Code	Product Code	Watts	Color Temp
7475	LED-FXHB200/40K/IP67	200W	4000K
7476	LED-FXHB200/50K/IP67	200W	5000K



14

IP65 Vapor Tight Premium



SKU Code	Product Code	Watts	Color Temp
7448	LED-FXVTL29/40K	29W	4000K
7449	LED-FXVTL29/50K	29W	5000K
7450	LED-FXVTL58/40K	58W	4000K
7451	LED-FXVTL58/50K	58W	5000K
7582	LED-FXVTL29/40K-SEN	29W	4000K
7583	LED-FXVTL29/50K-SEN	29W	5000K
7584	LED-FXVTL58/40K-SEN	58W	4000K
7585	LED-FXVTL58/50K-SEN	58W	5000K



15

Bulkhead Wall Light



SKU Code	Product Code	Watts	Color Temp
7024	LED-FXBWL10/830/BK	10W	3000K
7062	LED-FXBWL10/830/WH	10W	3000K
7025	LED-FXBWL10/850/BK	10W	5000K



16

Security Floodlight



SKU Code	Product Code	Watts	Color Temp
----------	--------------	-------	------------

Motion Sensor Included

7030	LED-FXBFD20/830/BK-SEN	20W	3000K
7031	LED-FXBFD20/850/BK-SEN	20W	5000K
7066	LED-FXBFD20/830/WH-SEN	20W	3000K
7067	LED-FXBFD20/850/WH-SEN	20W	5000K
7032	LED-FXSFD20/830/WH-SEN	20W	3000K
7033	LED-FXSFD20/850/WH-SEN	20W	5000K

Sensor Not Included

7082	LED-FXBFD20/830/BK	20W	3000K
7083	LED-FXBFD20/850/BK	20W	5000K



17

Direct / Indirect Decorative Wall Sconce



SKU Code	Product Code	Watts	Color Temp
----------	--------------	-------	------------

7026	LED-FXDWS10/830/BK	10W	3000K
7027	LED-FXDWS10/850/BK	10W	5000K
7068	LED-FXDWS10/830/WH	10W	3000K
7069	LED-FXDWS10/850/WH	10W	5000K
7064	LED-FXDWS20/830/BK	20W	3000K
7065	LED-FXDWS20/850/BK	20W	5000K
7070	LED-FXDWS20/830/WH	20W	3000K
7071	LED-FXDWS20/850/WH	20W	5000K



18

Security Lights C/W Photocell



SKU Code	Product Code	Watts	Color Temp
7190	LED-FXSECD28/40K	28W	4000K
7191	LED-FXSECD28/50K	28W	5000K
7477	LED-FXSECD38/40K	38W	4000K
7478	LED-FXSECD38/50K	38W	5000K
7140	LED-FXSECD37/40K	37W	4000K
7141	LED-FXSECD37/50K	37W	5000K
7136	LED-FXSECD20/40K	20W	4000K
7137	LED-FXSECD20/50K	20W	5000K
7414	LED-FXSECD13/40K	13W	4000K
7415	LED-FXSECD13/50K	13W	5000K
P10054	MT-DEA16 (Pole Arm)	-	-

See Accessories



19

Canopy & Parking Garage



SKU Code	Product Code	Watts	Color Temp
7166	LED-FXCCM40/40K/DB	40W	4000K
7167	LED-FXCCM40/50K/DB	40W	5000K
7538	LED-FXCCM40/40K/WH	40W	4000K
7539	LED-FXCCM40/50K/WH	40W	5000K
7084	LED-FXCCM60/40K/DB	60W	4000K
7085	LED-FXCCM60/50K/DB	60W	5000K
7538	LED-FXCCM40/40K/WH	40W	4000K
7539	LED-FXCCM40/50K/WH	40W	5000K
7536	LED-FXCCM60/40K/WH	60W	4000K
7537	LED-FXCCM60/50K/WH	60W	5000K
7090	LED-FXPG60/40K/DB	60W	4000K
7091	LED-FXPG60/50K/DB	60W	5000K



20

Slimline Canopy
Premium

SKU Code	Product Code	Watts	Color Temp
7468	LED-FXSCM28/40K/BK	28W	4000K
7469	LED-FXSCM28/50K/BK	28W	5000K
7495	LED-FXSCM28/40K/WH	28W	4000K
7496	LED-FXSCM28/50K/WH	28W	5000K
7489	LED-FXSCM28/40K/BK-SEN	28W	4000K
7490	LED-FXSCM28/50K/BK-SEN	28W	5000K
7470	LED-FXSCM42/40K/BK	42W	4000K
7471	LED-FXSCM42/50K/BK	42W	5000K
7497	LED-FXSCM42/40K/WH	42W	4000K
7498	LED-FXSCM42/50K/WH	42W	5000K
7491	LED-FXSCM42/40K/BK-SEN	42W	4000K
7492	LED-FXSCM42/50K/BK-SEN	42W	5000K
7472	LED-FXSCM59/40K/BK	59W	4000K
7473	LED-FXSCM59/50K/BK	59W	5000K
7499	LED-FXSCM59/40K/WH	59W	4000K
7500	LED-FXSCM59/50K/WH	59W	5000K
7493	LED-FXSCM59/40K/BK-SEN	59W	4000K
7494	LED-FXSCM59/50K/BK-SEN	59W	5000K



SKU Code	Product Code	Watts	Color Temp
7560	LED-FXSCM45/50K/BK-SEN	45W	5000K
7561	LED-FXSCM45/50K/WH-SEN	45W	5000K
7564	LED-FXSCM70/50K/BK-SEN	70W	5000K



21

Gas Station Canopy Premium



SKU Code	Product Code	Watts	Color Temp
7440	LED-FXGSC45/50K/WH	45W	5000K
7441	LED-FXGSC75/50K/WH	75W	5000K
7553	LED-FXGSC100/50K/WH	100W	5000K
7555	LED-FXGSC150/50K/WH	150W	5000K



22

WallPack TWP Forward Throw



*Visor Included



SKU Code	Product Code	Watts	Color Temp
7086	LED-FXTWP40/40K/DB	40W	4000K
7087	LED-FXTWP40/50K/DB	40W	5000K
7088	LED-FXTWP60/40K/DB	60W	4000K
7089	LED-FXTWP60/50K/DB	60W	5000K
7138	LED-FXTWP90/40K/DB	90W	4000K
7139	LED-FXTWP90/50K/DB	90W	5000K



23

WallPack
Forward ThrowDimmable
0-10V50,000
Rated
Life Hours

SKU Code	Product Code	Watts	Color Temp
* 7466	LED-FXTWP28/40K/DB	28W	4000K
* 7467	LED-FXTWP28/50K/DB	28W	5000K
7076	LED-FXTWP42/40K/DB	42W	4000K
7077	LED-FXTWP42/50K/DB	42W	5000K
7078	LED-FXTWP59/50K/DB	59W	4000K
7079	LED-FXTWP59/50K/DB	59W	5000K
7080	LED-FXTWP80/40K/DB	80W	4000K
7081	LED-FXTWP80/50K/DB	80W	5000K

*Visor Included See Accessories



24

WallPack
CWP Full CutoffDimmable
0-10V50,000
Rated
Life Hours

SKU Code	Product Code	Watts	Color Temp
7096	LED-FXCWP40/40K/DB	40W	4000K
7097	LED-FXCWP40/50K/DB	40W	5000K
7098	LED-FXCWP60/40K/DB	60W	4000K
7099	LED-FXCWP60/50K/DB	60W	5000K



25

WallPack SWP Slim Wall Pack



SKU Code	Product Code	Watts	Color Temp
7462	LED-FXSWP15/40K/BK	15W	4000K
7463	LED-FXSWP15/50K/BK	15W	5000K
7464	LED-FXSWP15/40K/WH	15W	4000K
7465	LED-FXSWP15/50K/WH	15W	5000K
7572	LED-FXSWP15/40K/DB	15W	4000K
7573	LED-FXSWP15/50K/DB	15W	5000K
7452	LED-FXSWP29/40K/BK	29W	4000K
7453	LED-FXSWP29/50K/BK	29W	5000K
7460	LED-FXSWP29/40K/WH	29W	4000K
7461	LED-FXSWP29/50K/WH	29W	5000K
7574	LED-FXSWP29/40K/DB	29W	4000K
7575	LED-FXSWP29/50K/DB	29W	5000K
7548	LED-FXSWP50/40K/BK	50W	4000K
7549	LED-FXSWP50/50K/BK	50W	5000K
7550	LED-FXSWP50/40K/WH	50W	4000K
7551	LED-FXSWP50/50K/WH	50W	5000K
7576	LED-FXSWP50/40K/DB	50W	4000K
7577	LED-FXSWP50/50K/DB	50W	5000K





SKU Code	Product Code	Watts	Color Temp
7112	LED-FXSB75/3S/40K/DB-SF	75W	4000K
7113	LED-FXSB75/3S/40K/DB-SB	75W	4000K
7114	LED-FXSB75/3S/40K/DB-EA6	75W	4000K
7115	LED-FXSB75/3S/50K/DB-SF	75W	5000K
7116	LED-FXSB75/3S/50K/DB-SB	75W	5000K
7117	LED-FXSB75/3S/50K/DB-EA6	75W	5000K
7118	LED-FXSB110/3S/40K/DB-SF	110W	4000K
7119	LED-FXSB110/3S/40K/DB-SB	110W	4000K
7120	LED-FXSB110/3S/40K/DB-EA6	110W	4000K
7121	LED-FXSB110/3S/50K/DB-SF	110W	5000K
7122	LED-FXSB110/3S/50K/DB-SB	110W	5000K
7123	LED-FXSB110/3S/50K/DB-EA6	110W	5000K
7176	LED-FXSB110/3S/50K/BK-EA6	110W	5000K
7169	LED-FXSB110/3S/50K/WH-EA6	110W	5000K
* 7192	LED-FXSB180/3S/40K/DB-SF	180W	4000K
* 7193	LED-FXSB180/3S/40K/DB-SB	180W	4000K
* 7194	LED-FXSB180/3S/40K/DB-EA6	180W	4000K
* 7195	LED-FXSB180/3S/50K/DB-SF	180W	5000K
* 7196	LED-FXSB180/3S/50K/DB-SB	180W	5000K
* 7197	LED-FXSB180/3S/50K/DB-EA6	180W	5000K
* 7400	LED-FXSB240/3S/40K/DB-SF	240W	4000K
* 7401	LED-FXSB240/3S/40K/DB-SB	240W	4000K
* 7402	LED-FXSB240/3S/40K/DB-EA6	240W	4000K
* 7403	LED-FXSB240/3S/50K/DB-SF	240W	5000K
* 7404	LED-FXSB240/3S/50K/DB-SB	240W	5000K
* 7405	LED-FXSB240/3S/50K/DB-EA6	240W	5000K

*DLC See Accessories






SKU Code	Product Code	Watts	Color Temp
7513	LED-FXFDL13/40K/BK	13W	4000K
7544	LED-FXFDL13/40K/WH	13W	4000K
7514	LED-FXFDL13/50K/BK	13W	5000K
7545	LED-FXFDL13/50K/WH	13W	5000K
7515	LED-FXFDL28/40K/BK	28W	4000K
7546	LED-FXFDL28/40K/WH	28W	4000K
7516	LED-FXFDL28/50K/BK	28W	5000K
7547	LED-FXFDL28/50K/WH	28W	5000K
7517	LED-FXFDL50/40K/BK	50W	4000K
7558	LED-FXFDL50/40K/WH	50W	4000K
7518	LED-FXFDL50/50K/BK	50W	5000K
7559	LED-FXFDL50/50K/WH	50W	5000K
7179	LED-FXFDL29/40K/DB-KNC	29W	4000K
7180	LED-FXFDL29/50K/DB-KNC	29W	5000K
7181	LED-FXFDL58/40K/DB-KNC	58W	4000K
7182	LED-FXFDL58/50K/DB-KNC	58W	5000K





ACCESSORIES



Turning Light into Savings ▶▶▶

01

Retrofit Recess Can
Accessories

SKU Code	Product Code	Color
P10029	ADP-RLGU24-N	-
P10057	RT-4RL-BK	Black
P10060	RT-6RL-BK	Black
P10058	RT-4RL-CH	Chrome
P10061	RT-6RL-CH	Chrome
P10082	RT-4RL-CH-WH	White
P10083	RT-6RL-CH-WH	White
P10059	RT-4RL-BZ	Bronze
P10062	RT-6RL-BZ	Bronze
P10084	RTS-4RL-WH	White
P10085	RTS-6RL-WH	White

Accessories for
Recessed Can



02

Shoebox/Area Light
Accessories

SKU Code	Product Code	Color
P10024	Slip Fitter	Dark Bronze
P10025	Swivel Bracket	Dark Bronze
P10026	6" Extruded Arm	Dark Bronze
P10046	4" Round pole adaptor	Dark Bronze
P10047	5" Round pole adaptor	Dark Bronze
P10048	6" Round pole adaptor	Dark Bronze
P10049	4" Round pole adaptor	White
P10050	5" Round pole adaptor	White
P10051	6" Round pole adaptor	White
P10054	Dusk to Dawn 16" Extension Arm Pole	-

Accessories for
Shoebox



03

Photocells



SKU Code	Product Code
P10036	SEN-PHO-BT-MT/MV
P10030	SEN-PHO-LK-MT/MV
P10053	SEN-PHO-LK-MT/SRT

MV = 120 - 277V

04

Sensors (Outdoor)



SKU Code	Product Code
P10038	SEN-LOS-501-SED
P10039	SEN-LOS-501-SPD
P10040	SEN-LOS-501-SEC
P10041	SEN-LOS-501-SPC
P10042	SEN-LOD-500-SED
P10043	SEN-LOD-500-SPD
P10044	SEN-LOD-500-SEC
P10045	SEN-LOD-500-SPC
P10091	SEN-MC605V-D (Microwave Sensor)

05

Slimline Wallpack
Accessories

SKU Code	Product Code	Color
P10005	MT-SB-SWP/BK	Black
P10074	MT-SB-SWP/BD	Dark Bronze
P10019	MT-SB-SWP/WH	White
P10006	MT-KNC-SWP/BK (3/4" NPT)	Black
P10075	MT-KNC-SWP/BD (3/4" NPT)	Dark Bronze
P10020	MT-KNC-SWP/WH (3/4" NPT)	White
P10007	MT-SF-SWP/BK	Black
P10076	MT-SF-SWP/BD	Dark Bronze
P10021	MT-SF-SWP/WH	White

Accessories for
Slim Wallpack 

06

TWP Shield



SKU Code	Product Code	Color
P10022	CVR-TWP40/DB	Dark Bronze
P10023	CVR-TWP60/DB	Dark Bronze

Accessories for
Traditional Wall Pack 

07

Sensor for Highbay



SKU Code	Product Code	
P10086	SEN-LOS-509-SFG	On-Off Aisle Lens
P10087	SEN-LOS-509-SFC	On-Off Area Lens
P10088	SEN-LOD-500-SFG	0-10V Aisle Lens
P10089	SEN-LOD-500-SFC	0-10V Area Lens

Accessories for
High Bay



08

Linear Highbay Accessories Yoke Mount & Wireguard



SKU Code	Product Code	Color
P10092	MT-YK-HBL22	Yoke Mount
P10093	MT-YK-HBL44	Yoke Mount
P10094	WG-HBL22/WH	Wireguard
P10095	WG-HBL44/WH	Wireguard

Accessories for
Linear High Bay



09

ON/OFF Switch / Pull Chain



SKU Code	Product Code	Color
P10077	SWCH-ZE109-NI (Pull Chain)	Nickel
P10078	SWCH-ZE204A (Toggle Switch)	White

Accessories for
Decorative Accent Vanity
FMM with Multi Voltage



10

Battery Back Up



SKU Code	Product Code	Voltage
7332	BAEM8.4-60/MV-B	120-277

Notes



natura**led**[®]



www.mynaturaLED.com

T: 909-930-6868

F: 909-930-9988