



PROGRESS LIGHTING
DESIGN+SERIES

2018



 **PROGRESS**
LIGHTING™



*INTRODUCING STATEMENT-
MAKING PIECES FROM OUR
DESIGN SERIES COLLECTION.*

Our Design Series fixtures feature artistic influence, fashion forward elements and details to contribute to affordable luxury for the home.

The fixtures found throughout the Design Series become the statement, the art piece and the focal point – and contribute to an overall luxurious experience in the home. They don't blend in. *They stand out.*

DESIGN+SERIES

*TABLE OF
CONTENTS*

4 Pictorial Index

14 Inspiration

44 Fixture Collections

144 Pendants



178 Sconces

188 Bath Collections

228 Outdoor



260 Index

FIXTURE COLLECTIONS

ALLAIRE
Antique Bronze p.51



ASPEN CREEK
Brushed Nickel p.95



ASTRA
Brushed Nickel p.71



ASTRA
Antique Bronze p.71



BERGAMO
Forged Bronze p.55



CAHILL
Brushed Bronze p.46



CORDIN
Brushed Nickel p.122



DEBUT
Brushed Nickel p.90



DEBUT
Graphite p.92



DESIREE
Silver Ridge p.49



DESIREE
Silver Ridge p.48




ELEVATE
Polished Chrome p.76



ELEVATE
Brushed Bronze p.74



EVOKE
Antique Bronze p.86



EVOKE
Polished Nickel p.88



FONTAYNE
Brushed Nickel p.100



FONTAYNE
Antique Bronze p.98



FONTAYNE
Brushed Nickel p.101



FONTAYNE
Antique Bronze p.99



FOTON
Graphite p.80



GLAYSE
Brushed Nickel p.63



GLAYSE
Antique Bronze p.65



GLIMMER
Antique Bronze p.59



GLIMMER
Silver Ridge p.59



GLIMMER
Antique Bronze p.60



GLIMMER
Silver Ridge p.60



HANGAR
Brushed Nickel p.67



HANGAR
Antique Bronze p.69



ION
Polished Nickel p.83



ION
Brushed Bronze p.83



LOOKING GLASS
Antique Bronze p.130



MARCHÉ
Polished Nickel p.112



FIXTURE COLLECTIONS (CONT'D)

METRIC
Brushed Nickel p.120



METRIC
Polished Chrome p.121



MOD
Polished Chrome p.78



MODERNA
Brushed Nickel p.169



NOMA
Antique Bronze p.108



NOMA
Polished Nickel p.110



PALACIO
Vintage Gold p.44



RATIO
Antique Bronze p.136



RATIO
Brushed Nickel p.137



REMIX
Graphite p.97



SAVOR
Silver Ridge p.114



SOIREE
Antique Bronze p.106



SPATIAL
Black p.73



SPICEWOOD
Gilded Iron p.104



SWAY
Antique Bronze p.56



TURNBURY
Galvanized Finish p.103



VESTIQUE
Graphite p.84



WEST VILLAGE
Brushed Nickel p.118



WEST VILLAGE
Antique Bronze p.116



PENDANTS

ALLAIRE
Antique Bronze p.53



ASPEN CREEK
Brushed Nickel p.95



ASSEMBLY HALL
Brushed Nickel p.125



ASSEMBLY HALL
Antique Bronze p.125



BEAKER
Polished Chrome p.140



BEAKER
Antique Bronze p.141



BERGAMO
Forged Bronze p.55



CAHILL
Brushed Bronze p.47



CAHILL
Brushed Bronze p.47



CAPTIVATE
Graphite p.129



CARBON
Polished Nickel p.162



CARBON
Graphite p.163



CAZBAH
Brushed Nickel p.159



CAZBAH
Antique Bronze p.158



CINQ
Antique Bronze p.139



CELESTE
Polished Nickel p.173



CELESTE
Polished Nickel p.172



CHRONICLE
Antique Bronze p.156



CHRONICLE
Polished Nickel p.157



CORDIN
Brushed Nickel p.123



DESIREE
Silver Ridge p.49



DESIREE
Silver Ridge p.49



ELLYSON
Polished Chrome p.145



ELLYSON
Brushed Bronze p.144




ERA
White p.161



ERA
Black p.160



FERMI
Brushed Nickel p.176



FINN
Black p.167



FINN
Metallic Silver p.166



FONTAYNE
Antique Bronze p.98



PENDANTS (CONT'D)

FONTAYNE
Brushed Nickel p.100



FONTAYNE
Antique Bronze p.99



FONTAYNE
Brushed Nickel p.101



GALLEY
Antique Bronze p.146



GALLEY
Polished Nickel p.147



GLIMMER
Antique Bronze p.60



GLIMMER
Silver Ridge p.60



GLIMMER
Antique Bronze p.61



GLIMMER
Silver Ridge p.61



GLAYSE
Antique Bronze p.65



GLAYSE
Brushed Nickel p.63



GLAYSE
Antique Bronze p.64



GLAYSE
Brushed Nickel p.62



GLAYSE
Antique Bronze p.65



GLAYSE
Brushed Nickel p.63



HANGAR
Antique Bronze p.69



HANGAR
Brushed Nickel p.67



HANGAR
Antique Bronze p.69



HANGAR
Brushed Nickel p.67



LOOKING GLASS
Antique Bronze p.131



MALBEC
Brushed Nickel p.152



MALBEC
Antique Bronze p.153



MALBEC
Graphite p.153



MARCHÉ
Polished Nickel p.113



MARQUE
Antique Bronze p.133



MARQUE
Graphite p.132



MESH
Antique Bronze p.164



MESH
Antique Bronze p.165



MOBI
Graphite p.148



MODERNA
Brushed Nickel p.169



NOMA
Polished Nickel p.111



NOMA
Antique Bronze p.109



OVERBROOK
Antique Bronze p.142



OVERBROOK
Silver Ridge p.143



PALACIO
Vintage Gold p.45



PALACIO
Vintage Gold p.45



PARLAY
Brushed Nickel p.171



PARLAY
Polished Chrome p.171



PARLAY
Antique Bronze p.170



RE-BAR
Polished Chrome p.174



REMIX
Graphite p.96



SAVOR
Silver Ridge p.115



SPATIAL
Black p.73



SPATIAL
Black p.73



SPICEWOOD
Gilded Iron p.105



SOIREE
Antique Bronze p.107



STAUNTON
Brushed Nickel p.151



STAUNTON
Antique Bronze p.151



STAUNTON
Graphite p.151



SWAY
Antique Bronze p.57



TURNBURY
Galvanized Finish p.103



VESTIQUE
Graphite p.85



WEMBERLY
Graphite p.135



WESTFALL
Antique Bronze p.127



WESTFALL
Graphite p.127



WEST VILLAGE
Antique Bronze p.117



WEST VILLAGE
Polished Nickel p.119



ZIN
Brushed Nickel p.155



ZIN
Antique Bronze p.155



ZIN
Graphite p.154



SCONCES / WALL BRACKETS

ALLAIRE

Antique Bronze p.52



ASPEN CREEK

Brushed Nickel p.95



ASTRA

Brushed Nickel p.71



ASTRA

Antique Bronze p.71



AVANA

Brushed Nickel p.182



AVANA

Antique Bronze p.183



AVANA

Polished Nickel p.183



BEAKER

Polished Chrome p.141



BEAKER

Antique Bronze p.141



BERGAMO

Forged Bronze p.55



BONITA

Brushed Nickel p.185



BONITA

Polished Chrome p.184



BONITA

Antique Bronze p.185



CAHILL

Brushed Bronze p.47



CAPTIVATE

Graphite p.129



CORDIN

Brushed Nickel p.123



DEBUT

Brushed Nickel p.91



DEBUT

Graphite p.93



DESIREE

Silver Ridge p.49



FORMES

Antique Bronze p.178



FORMES

Antique Bronze p.179



FORMES

Antique Bronze p.179



FOTON

Graphite p.81



FOTON

Graphite p.81



GLAYSE

Brushed Nickel p.63



GLAYSE

Antique Bronze p.65



GLIMMER

Antique Bronze p.61



GLIMMER

Silver Ridge p.61



HOBBS

Brushed Nickel p.187



HOBBS

Polished Chrome p.186



HOBBS
Antique Bronze p.187



LOOKING GLASS
Antique Bronze p.131



MARCHÉ
Polished Nickel p.113



METRO
Brushed Nickel p.181



METRO
Polished Chrome p.180



METRO
Antique Bronze p.181



MOD
Polished Chrome p.79



NOMA
Antique Bronze p.109



NOMA
Polished Nickel p.111



PALACIO
Vintage Gold p.45



SAVOR
Silver Ridge p.115



SOIREE
Antique Bronze p.107



SWAY
Antique Bronze p.57



VESTIQUE
Graphite p.85



VOLO
Brushed Nickel p.188



VOLO
Antique Bronze p.189



WEMBERLY
Graphite p.135



WEST VILLAGE
Brushed Nickel p.119



WEST VILLAGE
Antique Bronze p.117



ZURA
Brushed Nickel p.191



ZURA
Polished Chrome p.191



ZURA
Black p.190



BATH COLLECTIONS

CAHILL
Brushed Bronze p.202



CARYLYN
Antique Bronze p.215



CARYLYN
Polished Nickel p.215



DEBUT
Brushed Nickel p.207



DEBUT
Graphite p.206



ELEVATE
Polished Chrome p.77, 205



ELEVATE
Brushed Bronze p.75, 205



FLIGHT
Brushed Nickel p.210



FLIGHT
Polished Chrome p.211



GLANCE
Polished Chrome p.216



GLANCE
Antique Bronze p.217



GLAYSE
Brushed Nickel p.193



GLAYSE
Antique Bronze p.192



GLIDE
Brushed Nickel p.218



GLIDE
Polished Chrome p.220



GLIDE
Oil Rubbed Bronze p.221



LOGIC
Brushed Nickel p.208



LOGIC
Polished Chrome p.209



METRIC
Brushed Nickel p.226



METRIC
Polished Chrome p.227



MOD
Polished Chrome p.198




SOIREE
Antique Bronze p.201



SPATIAL
Black p.196



UNION SQUARE
Stainless Steel p.195



VOLO
Brushed Nickel p.189



BATH COLLECTIONS *(CONT'D)*

VOLO
Antique Bronze p.189



WANDER
Brushed Nickel p.222



WANDER
Polished Chrome p.224



WANDER
Venetian Bronze p.225



WEST VILLAGE
Brushed Nickel p.213



WEST VILLAGE
Antique Bronze p.213



OUTDOOR

ANDOVER GU24
Black p.241



CADENCE
Oil Rubbed Bronze p.231



CADENCE GU24
Black p.229



CRAWFORD GU24
Black p.239



CREIGHTON
Antique Bronze p.247



CREIGHTON
Black p.247



DEVEREUX
Antique Bronze p.243



GIBBES STREET
Antique Bronze p.251



HERMOSA
Black p.237



KIAWAH
Black p.257



MAISON GU24
Black p.233



PATEWOOD
Black p.255



SANTEE
Antique Bronze p.253



SANTEE
Black p.253



TWAIN
Antique Bronze p.259



UNION SQUARE
Stainless Steel p.248



VERDAE
Antique Bronze p.245



VERDAE
Black p.245



WHITACRE
Antique Bronze p.235





Featuring Bergamo chandelier, wall brackets, pendant and Hermosa lanterns.



*EVOKE STYLISH
STORYBOOK CHARM*

This space charms all five senses through soft color palettes, vintage pieces of furniture and floral accents. The beautiful detail of Hermosa's Mediterranean-style lanterns contribute visual interest while bringing traditional exterior fixtures indoors. Bergamo's two-toned frame and tassel accents enhance the textured ceilings, walls and accessories.

SWEET, SERENE & SOPHISTICATED

Celebrate a new addition's grand entrance with a nursery to match! Designers today are incorporating sophisticated and simple elements to create magical settings for children.

The furniture selection carries a monochromatic color scheme, while floral accents and textured accessories add character to the space shown. Marché collection pairs perfectly with Carlyn's luxurious pattern and glass accents to create a gorgeous nursery with a touch of glam.





COMPLEMENT CLASSIC DESIGNS

Classic forms, geometric patterns and mixed metal finishes work together to define this stunning living area, while also enhancing the soothing color palette. Westfall's dramatic soaring frame and candelabra cluster complement Soiree's tall candles and clear seeded glass, creating an overall inviting atmosphere.





Featuring Glimmer chandelier and Bonita wall sconce.

***EMBRACE
ELEGANCE &
SPARKLE***

To contrast the gray color scheme, rich furniture and sleek hardware, we chose lighting fixtures with glass accents, metal finishes and architecturally styled frames to bring intrigue and a sophisticated sparkle to the room.

A SERIES OF STATEMENT- MAKING FIXTURES

Bold geometric patterns and Glayse's unbounded beveled glass adds a quirky flair to the clean lines and functionality of this design.

Additionally, the use of glass creates a sense of connection to nature and the outdoors. Hangar's unique form and Astra's organic design serve as statement pieces to complete the look.





CREATE A SERENE RETREAT

We selected the Marché chandelier for this master bathroom because of its luxurious sheer silver organza shade and Polished Nickel finish. These sophisticated elements contrast nicely with the traditionally elegant Bonita wall sconce to complement luxurious living with an understated beauty. Finally, geometric tile and a neutral color scheme contributes to a spa-like environment for individuals to enjoy while either starting or ending their day.









*MIXED METALS
ARE HOT!*

Not only are finishes “heating up” but the freedom to mix metals is growing in popularity. Much like combining gold and silver jewelry, there isn’t a rule that commits you to one finish from room to room. How you curate and combine metal accents will enhance a luxurious setting.

Featuring Elevate chandelier



*PAIR SCULPTURAL
DESIGNS WITH
FARMHOUSE DÉCOR*

With a little country flair and an inviting atmosphere, this clean and simple design style is surging in popularity in homes across the nation. Rich tones and antique décor pair perfectly with the sculptural details featured in our Fermi and Re-Bar pendants. The lighting design also features a wall sconce and chandelier from our Cordin collection, which provides a playful contrast and creates a unique visual statement within the space.



Featuring Fermi pendant, Re-bar pendant, Cordin sconce and chandelier.



Featuring Savor chandelier and sconce.



UNWIND IN A ROMANTIC SETTING

This spa-inspired sanctuary encourages rest and relaxation. Romantic rose tones, plush furniture and natural light work to create the perfect environment to escape from the daily to do list. Our Savor chandelier and sconce contribute an essence of craftsmanship with contemporized wrought iron details and a sweeping profile.

BRING THE OUTDOORS IN

Size matters! When it comes to selecting fixtures for a particular room, oversized or exaggerated frames are on trend in a big way.

In lieu of table lamps, we've chosen sconces from our Union Square outdoor lantern collection – a unique way of bringing the “outdoors” inside! Finally, our oversized Turnbury chandelier creates a dramatic focal point for this luxurious bedroom.





Featuring Turnbury chandelier and Union Square wall lanterns.

SWOON OVER MID-CENTURY MODERN DESIGN

Our designers selected a series of statement fixtures, where each complements the next, to highlight this great room that features a variety of shapes and pops of color.

Hangar's light and airy form adds visual interest, while also providing a unique contrast to Astra's asymmetrical design. Inspired by the art of engineering, Spatial's geometric frame balances and completes the design scheme.





Featuring Spatial chandelier, Astra chandelier and Hangar pendants.



Featuring Looking Glass chandelier and Era pendants.



THE KEY TO COORDINATING

The key to coordinating lighting throughout the home is finding a good balance. Try to avoid choosing every light fixture from one particular collection.

Instead, select fixtures that feature similar metal profiles or design styles. While the Era pendant and Looking Glass chandelier are from different families, each contains elements with an overall vintage feel. Iron accents, hints of brass and mechanical details all work together to create a unique statement.

LAYER LIGHTING WITH GEOMETRIC ACCENTS

Circular elements featured in the mirror and Debut chandelier work together to provide dramatic focal points to this living space. Additionally, the Squire outdoor wall lantern was incorporated in a creative way in this interior setting to create a rich layer of light to contribute to the room's décor.





Featuring Ion chandelier.

***PERSONALIZE
TRENDS TO MAKE
IT YOUR OWN***

Keep in mind, a light fixture is not going to define your style. It's all about how your light fixture fits into your personalized living space. You can make a home feel more luxurious because of the product you are putting into it so get creative and design with what you like.



Featuring Zura™ sconces.

COORDINATE with DELTA® BATH MATCH

One of the most important things to remember when illuminating your bathroom is to provide shadow-free lighting at the mirror. This bath area benefits from a generous amount of natural light, while our sleek and sophisticated Zura™ sconces placed on either side of the bathroom mirror work to further reduce shadows on the side of the face.



EARTH TONES TRENDING

Earthy granites and similar tones can make a big statement within a room. Additionally, Walnut is making a comeback because of the popularity of the mid-century modern design.

Featuring Cinq pendant.



Featuring Desiree pendants and sconces.



ALL THAT GLITTERS FOR A GLAMOROUS DESIGN

When friends and family walk into this glamorous foyer, they will instantly fall in love with the lighting design presented.

This grouping of pendants from the Desiree collection features luxury materials and details reminiscent of Hollywood's "Golden Era." A Silver Ridge finish and clear crystal strands cascade in a waterfall effect to convey the glitz and glamour from an iconic time that is making a modern comeback.



MARBLE, GLASS & GOLD – OH MY!

Everyone deserves a little bit of luxe in his or her home. Sleek design, nature-inspired elements and ornate details make a statement within this lavishly designed setting. Our Palacio fixtures pair a Vintage Gold finish with faux white marble accents that complement the sophisticated glass spheres found in the Ellyson pendants.



Featuring Palacio chandelier and foyer, Cahill sconces and Ellyson pendants.

PALACIO NEW

An intriguing fashion-forward lighting collection, Palacio pairs a Vintage Gold finish with faux white marble accents for a stunningly elegant design. White silk shades complement gold accents to create a statement-making style. Ideal for a variety of interiors.



P400098-078



P500108-078



P500105-078

FINISH

● Vintage Gold - 078

FIVE-LIGHT CHANDELIER

P400098-078 Vintage Gold
27" dia., 21-1/2" ht.
Overall ht. w/chain 96-1/2", wire 15'.
Five medium base lamps,
75w max. each

NINE-LIGHT CHANDELIER

P400099-078 Vintage Gold
36" dia., 25" ht.
Overall ht. w/chain 148", wire 15'.
Nine medium base lamps,
each 75w max.

FOUR-LIGHT FOYER PENDANT

P500105-078 Vintage Gold
15" Sq., 26-1/2" ht.
Overall ht. w/chain 110", wire 15'.
Four candelabra base lamps,
each 60w max.



P400098-078



P500106-078

EIGHT-LIGHT FOYER

P500106-078 Vintage Gold
20" dia., 30-1/2" ht.
Overall ht. w/chain 113-1/2", wire 15'.
Eight candelabra base lamps,
each 60w max.

MINI-PENDANT

P500107-078 Vintage Gold
8" dia., 17" ht.
Overall ht. w/stem 83", wire 10'.
One medium base lamp,
75w max. each

FOUR-LIGHT PENDANT

P500108-078 Vintage Gold
22" dia., 9-5/8" ht.
Overall ht. w/stem 73", wire 10'.
Four candelabra base lamps,
each 60w max.

WALL BRACKET

P710037-078 Vintage Gold
6" W., 17" ht.
Extends 7-1/2". H/CTR 9".
One medium base lamp,
75w max.



P400099-078



P500107-078



P710037-078

CAHILL

NEW

A stylish Brushed Bronze finish frames brilliant clear beveled glass panels in the Cahill collection. Ideal for Luxe or Mid-Century Modern interiors, the visual interest provides a reinvention of the popular glass design.



ALSO AVAILABLE IN
Bath & Vanity, page 202



P400071-109



P500075-109



P300108-109

FINISH

● Brushed Bronze - 109

ONE-LIGHT BATH

P300108-109 Brushed Bronze
4-1/2" W., 19-3/4" ht.
Overall ht. w/chain 9-3/4"
Extends 7-1/2".
One candelabra base lamp,
60w max.

FIVE-LIGHT CHANDELIER

P400071-109 Brushed Bronze
25-5/8" dia., 13" ht.
Overall ht. w/chain 70", wire 15'.
Five candelabra base lamps,
each 60w max.



P500076-109



P400071-109

EIGHT-LIGHT CHANDELIER

P400072-109 Brushed Bronze
31-3/8" dia., 13-5/8" ht.
Overall ht. w/chain 69-1/2", wire 15'.
Eight candelabra base lamps,
each 60w max.

MINI-PENDANT

P500075-109 Brushed Bronze
7-3/4" dia., 17-5/8" ht.
Overall ht. w/chain 75", wire 10'.
One medium base lamp,
60w max.

FOUR-LIGHT PENDANT

P500076-109 Brushed Bronze
15-3/4" dia., 19-3/4" ht.
Overall ht. w/chain 78-1/2", wire 10'.
Four candelabra base lamps,
each 60w max.



P500077-109



P400072-109

SIX-LIGHT PENDANT

P500077-109 Brushed Bronze
18" dia., 24-1/2" ht.
Overall ht. w/chain 81", wire 10'.
Six candelabra base lamps,
each 60w max.

*Shown with P7826-01
vintage lamps*

DESIREE NEW

The Desiree collection features luxury materials and details reminiscent of Hollywood's Regency period. A Silver Ridge finish and clear crystal strands cascade in a waterfall effect to convey the glitz and glamour from an iconic time that is making a modern comeback.



P400079-134



P350106-134



P500085-134

FINISH

- Silver Ridge - 134

SEMI-FLUSH CONVERTIBLE

P350106-134 Silver Ridge
Hanging and ceiling mount hardware included.
15-7/8" dia., 14" ht.
Overall ht. w/chain 53", wire 10'.
Three candelabra base lamps, each 60w max.

FIVE-LIGHT CHANDELIER

P400078-134 Silver Ridge
28" dia., 24" ht.
Overall ht. w/chain 99", wire 15'.
Five candelabra base lamps, each 60w max.



P400078-134



P500086-134

SIX-LIGHT LINEAR CHANDELIER

P400079-134 Silver Ridge
38" W., 13-3/4" ht.
Overall ht. w/chain 103-3/4", wire 15'.
Extends 12".
Six candelabra base lamps, each 60w max.

EIGHT-LIGHT CHANDELIER

P400100-134 Silver Ridge
36" dia., 30-3/4" ht.
Overall ht. w/chain 106", wire 15'.
Eight candelabra base lamps, each 60w max.



P400100-134

THREE-LIGHT PENDANT

P500085-134 Silver Ridge
13-7/8" dia., 19-3/8" ht.
Overall ht. w/chain 94-1/2", wire 15'.
Three candelabra base lamps, each 60w max.

SIX-LIGHT PENDANT

P500086-134 Silver Ridge
17-7/8" dia., 29" ht.
Overall ht. w/chain 104", wire 15'.
Six candelabra base lamps, each 60w max.

WALL SCONCE

P710030-134 Silver Ridge
8-1/4" W., 13-5/8" ht.
Extends 5-3/8". H/CTR 6-3/4".
One candelabra base lamp, 60w max.



P710030-134

ALLAIRE

Alternating oval and round vintage beads create beautiful strands that are completed by a large faceted glass pendalogue. Champagne candles and an Antique Bronze finish add to the sophisticated design details. Two shade styles, both featuring a rich Espresso trim, are available as accessories.



P400004-020 with
P860000-001 shade

FINISHES

- Antique Bronze - 020

FIVE-LIGHT CHANDELIER

P400004-020 Antique Bronze
 26" dia., 30-3/4" ht.
 Overall ht. w/chain 108-1/2"; wire 15'.
 Five candelabra base lamps,
 each 60w max.

ACCESSORY SHADE

P860000-001 Champagne
 silk with espresso trim.
 1" uno-style candle fitter.
 5" dia., 5" ht.

ACCESSORY SHADE

P860001-001 Champagne
 organza with espresso trim.
 1" uno-style candle fitter.
 5" dia., 5" ht.



P860001-001



P860000-001

ALLAIRE

FINISHES

● Antique Bronze - 020

SEMI-FLUSH CONVERTIBLE

P350030-020 Antique Bronze
Hanging and ceiling mount hardware included. Accessory shades do not fit fixture.
16" dia., 12-7/8" ht.
Overall ht. w/chain 52"; wire 10'.
Three candelabra base lamps, each 60w max.



P710003-020

EIGHT-LIGHT CHANDELIER

P400005-020 Antique Bronze
32" dia., 31" ht.
Overall ht. w/chain 108-1/2"; wire 15'.
Eight candelabra base lamps, each 60w max.



P400005-020

NINE-LIGHT CHANDELIER

P400006-020 Antique Bronze
32" dia., 35" ht.
Overall ht. w/chain 160"; wire 15'.
Nine candelabra base lamps, each 60w max.



P710003-020
shown with
P860000-001 shade

WALL BRACKET

P710003-020 Antique Bronze
5-1/8" W., 20-5/8" ht.
Extends 6-3/4". H/CTR 12".
One candelabra base lamp, 60w max.



P710003-020
shown with
P860001-001 shade



P400005-020
shown with
P860001-001 shade



P400005-020
shown with
P860000-001 shade



BERGAMO NEW

Bergamo features an elegant wispieness within a two-toned frame. Weathered stone accents and tassel details create a relaxed, rustic casual collection. These versatile pieces can be incorporated over a dining room table in a Rustic Farmhouse setting or in a Transitional open living space. Wall bracket, chandelier and foyer fixture options are available.



P400068-077



FINISH

● Forged Bronze - 077

FIVE-LIGHT CHANDELIER
P400068-077 Forged Bronze
 26" dia., 27-7/8" ht.
 Overall ht. w/chain 103", wire 15'.
 Five candelabra base lamps,
 each 60w max.

SIX-LIGHT CHANDELIER
P400069-077 Forged Bronze
 32" dia., 33-3/8" ht.
 Overall ht. w/chain 108-1/2", wire 15'.
 Six candelabra base lamps,
 each 60w max.



TWELVE-LIGHT CHANDELIER
P400070-077 Forged Bronze
 42-1/8" dia., 46-7/8" ht.
 Overall ht. w/chain 170", wire 15'.
 Twelve candelabra base lamps,
 each 60w max.

FOUR-LIGHT FOYER PENDANT
P500091-077 Forged Bronze
 18-3/4" dia., 42-1/8" ht.
 Overall ht. w/chain 117-1/2", wire 15'.
 Four candelabra base lamps,
 each 60w max.

WALL BRACKET

P710032-077 Forged Bronze
 6" W., 17-1/4" ht.
 Extends 7-5/8". H/CTR 6".
 One candelabra base lamp,
 60w max.



SWAY

Alternating lengths of elongated clear glass teardrops are elegantly displayed across a circular Antique Bronze frame. An artistic fixture, Sway's artisanal glass accents are handmade to feature unique variations.



P400007-020



P710004-020



P500005-020

FINISHES

- Antique Bronze - 020

SEMI-FLUSH CONVERTIBLE

P350031-020 Antique Bronze
Hanging and ceiling mount hardware included.
13-5/8" dia., 15-7/8" ht.
Overall ht. w/chain 82"; wire 10'.
Three medium base lamps, each 60w max.

FIVE-LIGHT CHANDELIER

P400007-020 Antique Bronze
23" dia., 27-3/4" ht.
Overall ht. w/chain 93"; wire 15'.
Five medium base lamps, each 60w max.

MINI-PENDANT

P500005-020 Antique Bronze
6-7/8" dia., 10-3/4" ht.
Overall ht. w/chain 77"; wire 10'.
One medium base lamp, 60w max.

WALL BRACKET

P710004-020 Antique Bronze
6-7/8" W., 17-1/8" ht.
Extends 8-1/8". H/CTR 8-3/8".
One medium base lamp, 60w max.

Fixtures shown with P7827-01 vintage lamps.



P350031-020



P350031-020

GLIMMER

Elements that sparkle create an instant statement within the home - Glimmer fits the definition of livable luxury. Prismatic glass pendants are supported by an architecturally styled frame in Silver Ridge or Antique Bronze finishes.



P5321-134



P2326-134



P2326-20

FINISHES

- Antique Bronze - 20
- Silver Ridge - 134

SEMI-FLUSH CONVERTIBLE

P2326-20 Antique Bronze
P2326-134 Silver Ridge
 Hanging and ceiling mount hardware included.
 16-1/4" dia., 19" ht.
 Overall ht. w/chain 96-1/2", wire 10'.
 Three candelabra base lamps, each 60w max.

FIVE-LIGHT PENDANT

P5321-20 Antique Bronze
P5321-134 Silver Ridge
 22-1/4" dia., 23-7/8" ht.
 Overall ht. w/chain 99", wire 10'.
 Five candelabra base lamps, each 60w max.



P5321-134



P5321-20

SIX-LIGHT PENDANT

P5346-134 Silver Ridge
P5346-20 Antique Bronze
 28" dia., 29-1/4" ht.
 Overall ht. w/chain 104-1/2", wire 10'.
 Six candelabra base lamps, each 60w max.



P5346-134



P5346-20



New Product

GLIMMER

NEW

FINISHES

- Antique Bronze - 020
- Silver Ridge - 134

SEMI-FLUSH CONVERTIBLE

P350058-020 Antique Bronze
P350058-134 Silver Ridge
Hanging and ceiling mount hardware included.
13-5/8" Sq., 11-1/8" ht.
Overall ht. w/stem 49-1/2", wire 10'.
Two medium base lamps, each 60w max.



P350058-020



P350058-134

FOUR-LIGHT LINEAR CHANDELIER

P400101-020 Antique Bronze
P400101-134 Silver Ridge
33-7/8" W., 11-1/2" L. 11" ht.
Overall ht. w/stem 76", wire 15'.
Four medium base lamps, each 60w max.



P500109-020



P500109-134

FOUR-LIGHT PENDANT

P500109-020 Antique Bronze
P500109-134 Silver Ridge
20-1/8" Sq., 11" ht.
Overall ht. w/stem 77", wire 10'.
Four medium base lamps, each 60w max.



P400101-020



P400101-134

GLIMMER



FINISHES

- Antique Bronze - 020
- Silver Ridge - 134

SEMI-FLUSH CONVERTIBLE

P2325-20 Antique Bronze
P2325-134 Silver Ridge
 Hanging and ceiling mount hardware included.
 13-1/8" dia., 15-1/2" ht.
 Overall ht. w/chain 94", wire 10'.
 Three candelabra base lamps, each 60w max.

ONE-LIGHT MINI-PENDANT

P5320-20 Antique Bronze
P5320-134 Silver Ridge
 Includes one 6" stem, four 12" stems and 6 links of chain.
 6" dia., 11-1/4" ht.
 Overall ht. w/stem 77-1/2", wire 10'.
 One medium base lamp, 100w max.

WALL SCONCE

P7198-134 Silver Ridge
P7198-20 Antique Bronze
 8" W., 10" ht.
 Extends 4-3/4". H/CTR 3-1/2".
 Two candelabra base lamps, each 60w max.

GLAYSE NEW

Inspired by modern architecture, Glayse features handsome details for variety of interior design styles. The frameless unbounded beveled glass creates beautiful light and reflection. The structure of Glayse is the focal point of the design, where form follows function.



ALSO AVAILABLE IN
Bath & Vanity, page 192



P500095-020



P350090-009



P500073-009

FINISHES

- Brushed Nickel - 09

WALL SCONCE

P300105-009 Brushed Nickel
7" W., 8-3/8" ht.
Extends 5-1/2". H/CTR 5-3/8".
One medium base lamp,
60w max.

SEMI-FLUSH CONVERTIBLE

P350090-009 Brushed Nickel
Hanging and ceiling mount
hardware included.
16-3/4" Sq., 14-3/4" ht.
Overall ht. w/chain 80", wire 10'.
Four medium base lamps,
each 60w max.



P500074-009



P500095-009

FIVE-LIGHT LINEAR CHANDELIER

P400116-009 Brushed Nickel
36-3/4" W., 10" L., 15-3/4" ht.
Overall ht. w/stem 82", wire 15'.
Five medium base lamps,
each 60w max.

MINI-PENDANT

P500073-009 Brushed Nickel
6-1/2" Sq., 11-7/8" ht.
Overall ht. w/stem 77", wire 10'.
One medium base lamp,
60w max.

FIVE-LIGHT PENDANT

P500074-009 Brushed Nickel
22-3/4" Sq., 13-3/4" ht.
Overall ht. w/chain 80, wire 15'.
Five medium base lamps,
each 60w max.

FOUR-LIGHT FOYER PENDANT

P500095-009 Brushed Nickel
14-3/4" W., 28-3/8" ht.
Overall ht. w/stem 94-1/2", wire 15'.
Four medium base lamps,
each 60w max.



P400116-009



P300105-009

*Fixtures shown with P7825-01
vintage lamps.*



P500095-020

NEW

GLAYSE



FINISHES

- Antique Bronze - 20

WALL SCONCE

P300105-009 Brushed Nickel
7" W., 8-3/8" ht.
Extends 5-1/2". H/CTR 5-3/8".
One medium base lamp,
60w max.

SEMI-FLUSH CONVERTIBLE

P350090-020 Antique Bronze
Hanging and ceiling mount
hardware included.
16-3/4" Sq., 14-3/4" ht.
Overall ht. w/chain 80", wire 10'.
Four medium base lamps,
each 60w max.



FIVE-LIGHT LINEAR CHANDELIER

P400116-020 Antique Bronze
36-3/4" W., 10" L., 15-3/4" ht.
Overall ht. w/stem 82", wire 15'.
Five medium base lamps,
each 60w max.

MINI-PENDANT

P500073-020 Antique Bronze
6-1/2" Sq., 11-7/8" ht.
Overall ht. w/stem 77", wire 10'.
One medium base lamp,
60w max.

FIVE-LIGHT PENDANT

P500074-020 Antique Bronze
22-3/4" Sq., 13-3/4" ht.
Overall ht. w/chain 80, wire 15'.
Five medium base lamps,
each 60w max.

FOUR-LIGHT FOYER PENDANT

P500095-020 Antique Bronze
14-3/4" W., 28-3/8" ht.
Overall ht. w/stem 94-1/2", wire 15'.
Four medium base lamps,
each 60w max.

*Fixtures shown with P7825-01
vintage lamps.*



HANGAR NEW

Fixtures in the Hangar collection are fun, light and airy pieces – perfect for both casual and modern homes. A sophisticated, statement-making frame occupies a large visual space. Modern wire basket forms are finished in Brushed Nickel with graphite accents or Antique Bronze and natural brass accents to complete the design.



P500117-009



FINISHES

- Brushed Nickel - 009

SEMI-FLUSH CONVERTIBLE

P350102-009 Brushed Nickel
Hanging and ceiling mount hardware included. Vintage Linen Shade.
16" dia., 13-1/4" ht.
Overall ht. w/stem 78-1/2", wire 10'.
Two medium base lamps,
each 60w max.

FIVE-LIGHT CHANDELIER

P400105-009 Brushed Nickel
30" dia., 19-3/4" ht.
Overall ht. w/stem 77", wire 15'.
Five medium base lamps,
each 60w max.

EIGHT-LIGHT CHANDELIER

P400106-009 Brushed Nickel
40" dia., 24-7/8" ht.
Overall ht. w/stem 91-1/2", wire 15'.
Eight medium base lamps,
each 60w max.

MINI-PENDANT

P500115-009 Brushed Nickel
13" dia., 9-5/8" ht.
Overall ht. w/stem 76-1/2", wire 10'.
One medium base lamp,
60w max.

ONE-LIGHT PENDANT


P500116-009 Brushed Nickel
Vintage Linen Shade.
20" dia., 26" ht.
Overall ht. w/stem 92", wire 15'.
One medium base lamp,
100w max.

THREE-LIGHT PENDANT

P500117-009 Brushed Nickel
Vintage Linen Shade.
24" dia., 24-1/4" ht.
Overall ht. w/stem 90", wire 15'.
Three medium base lamps,
each 75w max.

WALL BRACKET

P710043-009 Brushed Nickel
5" W., 8-3/4" ht.
Extends 4-1/2". H/CTR 4".
One medium base lamp,
60w max.





P500117-020

P500115-020

shown with P7825-01
vintage lamp

P710043-020

FINISHES

- Antique Bronze - 020

SEMI-FLUSH CONVERTIBLE

P350102-020 Brushed Nickel
Hanging and ceiling mount hardware
included. Vintage Linen Shade.
16" dia., 13-1/4" ht.
Overall ht. w/stem 78-1/2", wire 10'.
Two medium base lamps,
each 60w max.

FIVE-LIGHT CHANDELIER

P400105-020 Antique Bronze
30" dia., 19-3/4" ht.
Overall ht. w/stem 77", wire 15'.
Five medium base lamps,
each 60w max.

EIGHT-LIGHT CHANDELIER

P400106-020 Antique Bronze
40" dia., 24-7/8" ht.
Overall ht. w/stem 91-1/2", wire 15'.
Eight medium base lamps,
each 60w max.

MINI-PENDANT

P500115-020 Antique Bronze
13" dia., 9-5/8" ht.
Overall ht. w/stem 76-1/2", wire 10'.
One medium base lamp,
60w max.

ONE-LIGHT PENDANT

P500116-020 Antique Bronze
Vintage Linen Shade.
20" dia., 26" ht.
Overall ht. w/stem 92", wire 15'.
One medium base lamp,
100w max.

THREE-LIGHT PENDANT

P500117-020 Antique Bronze
Vintage Linen Shade.
24" dia., 24-1/4" ht.
Overall ht. w/stem 90", wire 15'.
Three medium base lamps,
each 75w max.

WALL BRACKET

P710043-020 Antique Bronze
5" W., 8-3/4" ht.
Extends 4-1/2". H/CTR 4".
One medium base lamp,
60w max.

P400105-020

shown with P7825-01
vintage lamp

P350102-020



P400106-020

shown with P7827-01
vintage lamp

P500116-020



ASTRA NEW

An iconic fixture, Astra features an organic, asymmetrical design. Ideal for dining room settings or entryways, these classic Mid-Century inspired pieces are so versatile they can be incorporated into a variety of interiors.



P400108-009



FINISHES

- Brushed Nickel - 009
- Antique Bronze - 020

SIX-LIGHT CHANDELIER

P400108-009 Brushed Nickel
P400108-020 Antique Bronze
 22-5/8" dia., 10-1/2" ht.
 Overall ht. w/stem 72", wire 15'.
 Six medium base lamps,
 each 60w max.



EIGHT-LIGHT CHANDELIER

P400109-009 Brushed Nickel
P400109-020 Antique Bronze
 42-3/8" dia., 19-5/8" ht.
 Overall ht. w/stem 77", wire 15'.
 Eight medium base lamps,
 each 60w max.

WALL BRACKET

P710027-009 Brushed Nickel
P710027-020 Antique Bronze
 7-1/4" W., 17-3/4" ht.
 Extends 3-7/8". H/CTR 7".
 Two medium base lamps,
 each 60w max.

Fixtures shown with P7826-01 vintage lamps.



SPATIAL NEW

Spatial showcases a modern form that complements Urban Industrial, Mid-Century Modern and Bohemian styles. Overscale geometric frames feature designs inspired by metal trusses and the art of engineering. Matte Black finish is highlighted by clear globe shades or open candles. Chandelier and pendant options are ideal for foyers and entryways, while vanity fixtures complement modern spa-like bath suites.



ALSO AVAILABLE IN
Bath & Vanity, page 196



P500083-031
*shown with P7826-01
vintage lamp*



P500082-031
shown with P7827-01
vintage lamp



P400077-031

FINISHES

● Black - 31

SEMI-FLUSH CONVERTIBLE

P400077-031 Black
Hanging and ceiling mount hardware included.
19-5/8" dia., 14" ht.
Overall ht. w/chain 52", wire 10'.
Three candelabra base lamps, each 60w max.

SIX-LIGHT CHANDELIER

P400084-031 Black
26" dia., 32" ht.
Overall ht. w/chain 101", wire 15'.
Six medium base lamps, each 60w max.



P500083-031
shown with P7826-01
vintage lamp



P500096-031

MINI-PENDANT

P500082-031 Black
12" dia., 11-1/4" ht.
Overall ht. w/chain 85", wire 10'.
One medium base lamp, 100w max.

FOUR-LIGHT PENDANT

P500083-031 Black
23-1/2" dia., 19" ht.
Overall ht. w/chain 93-1/2", wire 15'.
Four candelabra base lamps, each 60w max.

SIX-LIGHT PENDANT

P500084-031 Black
28" dia., 26" ht.
Overall ht. w/chain 101", wire 15'.
Six candelabra base lamps, each 60w max.



P500084-031
shown with P7826-01
vintage lamp



P400084-031

THREE-LIGHT FOYER

P500096-031 Black
23-3/4" dia., 25-1/2" ht.
Overall ht. w/chain 100-1/2", wire 15'.
Three candelabra base lamps, each 60w max.

ELEVATE

Achieve a mid-century modern look with Elevate, which boasts glass shades and a frame inspired by Space Age styling. Brushed Bronze and Polished Chrome finish options available. Chandeliers feature fun and playful trapezoidal form.



ALSO AVAILABLE IN
Bath & Vanity, page 204



P400022-109



P350040-109



P350105-109-30



P300020-109



P400021-109

P400022-109



P400023-109



FINISH

- Brushed Bronze - 109

ONE-LIGHT WALL BRACKET

P300020-109 Brushed Bronze
5" W., 8" ht.
Extends 7". H/CTR 4".
One medium base lamp,
100w max.

THREE-LIGHT SEMI-FLUSH

P350040-109 Brushed Bronze
11-3/4" dia., 9-7/8" ht.
Three medium base lamps,
each 75w max.

ONE-LIGHT FLUSH MOUNT

P350105-109-30 Brushed Bronze
13" dia., 5-1/4" ht.
One 17W LED module, 3000K,
90 CRI, 1452 lumens.



THREE-LIGHT CHANDELIER

P400021-109 Brushed Bronze
21-3/4" dia., 23" ht.
Overall ht. w/stem 89"; wire 15'.
Three medium base lamps,
each 100w max.

FIVE-LIGHT CHANDELIER

P400022-109 Brushed Bronze
27-3/8" dia., 23" ht.
Overall ht. w/stem 89"; wire 15'.
Five medium base lamps,
each 100w max.

SEVEN-LIGHT CHANDELIER

P400023-109 Brushed Bronze
32-5/8" dia., 22-7/8" ht.
Overall ht. w/stem 89"; wire 15'.
Seven medium base lamps,
each 100w max.





P400022-109

ELEVATE



P350040-015



P350105-015-30



P300020-015



P400021-015



P400022-015



P400023-015

FINISH

- Polished Chrome - 015

ONE-LIGHT WALL BRACKET

P300020-015 Polished Chrome
5" W., 8" ht.
Extends 7". H/CTR 4".
One medium base lamp,
100w max.

THREE-LIGHT SEMI-FLUSH

P350040-015 Polished Chrome
11-3/4" dia., 9-7/8" ht.
Three medium base lamps,
each 75w max.

ONE-LIGHT FLUSH MOUNT

P350105-015-30 Polished Chrome
13" dia., 5-1/4" ht.
One 17W LED module, 3000K,
90 CRI, 1452 lumens.



THREE-LIGHT CHANDELIER

P400021-015 Polished Chrome
21-3/4" dia., 23" ht.
Overall ht. w/stem 89"; wire 15'.
Three medium base lamps,
each 100w max.

FIVE-LIGHT CHANDELIER

P400022-015 Polished Chrome
27-3/8" dia., 23" ht.
Overall ht. w/stem 89"; wire 15'.
Five medium base lamps,
each 100w max.

SEVEN-LIGHT CHANDELIER

P400023-015 Polished Chrome
32-5/8" dia., 22-7/8" ht.
Overall ht. w/stem 89"; wire 15'.
Seven medium base lamps,
each 100w max.

New Product

MOD

Giving a nod to the space age with mid-century modern appeal, Mod features a sleek linear frame in a Polished Chrome finish. Clear, spherical glass shades offer the perfect focal point for vintage bulbs or reflector-style globes.



ALSO AVAILABLE IN

Bath & Vanity, page 198



P4755-15



P2850-15

FINISH

- Polished Chrome - 15

WALL BRACKET

P2850-15 Polished Chrome
 5-7/8" W., 7-3/4" ht.
 Extends 7-3/8". H/CTR 3-7/8".
 One candelabra base lamp,
 60w max.

P4755-15



FIVE-LIGHT CHANDELIER

P4755-15 Polished Chrome
 28-7/8" dia., 19-7/8" ht.
 Overall ht. w/stem 86", wire 15'.
 Five candelabra base lamps
 each, 60w max.

SIX-LIGHT CHANDELIER

P4756-15 Polished Chrome
 34" dia., 24-7/8" ht.
 Overall ht. w/stem 91", wire 15'.
 Six candelabra base lamps
 each, 60w max.


P4756-15



*Fixtures shown with P7827-01
 vintage lamps.*

FOTON

Illuminate your home with bright designs inspired by the atomic age. This collection emulates a Mid-Century Modern style made popular in the 50's and 60's. The Graphite frame in Foton is accented with Brushed Nickel spherical accents. Available in chandelier, mini-pendant and wall bracket options.



P400019-143
shown with P7826-01
vintage lamps



P500015-143



P500015-143
wall mount with
P7826-01 vintage lamps



P500015-143



P400019-143



P710006-143
shown with P7826-01
vintage lamps



P400020-143
shown with P7826-01
vintage lamps

FINISH

- Graphite - 143

FIVE-LIGHT CHANDELIER

P400019-143 Graphite
24" dia., 7-5/8" ht.
Overall ht. w/stem 73-1/2"; wire 15'.
Five candelabra base lamps,
each 40w max.

SEVEN-LIGHT CHANDELIER

P400020-143 Graphite
32" dia., 7-5/8" ht.
Overall ht. w/stem 73-1/2"; wire 15'.
Seven candelabra base lamps,
each 40w max.

SEMI-FLUSH CONVERTIBLE

P500015-143 Graphite
Hanging and ceiling mount
hardware included.
12-3/4" dia., 3-3/4" ht.
Overall ht. w/stem 70"; wire 10'.
Three candelabra base lamps,
each 40w max.

WALL BRACKET

P710006-143 Graphite
5-1/8" W., 8-3/8" ht.
Extends 4". H/CTR 5-7/8".
One candelabra base lamp,
40w max.

ION

Featuring a Polished Nickel or Brushed Bronze finish, these Space-Age inspired chandeliers boast either twelve or sixteen lights, each extending to support a single candelabra base lamp. Additionally, Ion chandeliers pair with Progress Lighting's Elevate collection for stunning Mid-Century inspired interiors.



P400040-109



FINISHES

- Polished Nickel - 104
- Brushed Bronze - 109


TWELVE-LIGHT CHANDELIER

P400040-104 Polished Nickel
P400040-109 Brushed Bronze
 14-1/8" dia.,*
 Overall ht. w/stem 76"; wire 15'.
 Twelve candelabra base lamps,
 each 25w max.

SIXTEEN-LIGHT CHANDELIER

P400041-104 Polished Nickel
P400041-109 Brushed Bronze
 24" dia.,*
 Overall ht. w/stem 79-1/2"; wire 15'.
 Sixteen candelabra base lamps,
 each 25w max.

**Fixtures dimension does not include lamps.*



VESTIQUE

Vestique features a dazzling array of glass spheres suspended within a modern frame. Light artfully reflects and refracts through these elements to provide a dramatic focal point to any room.



P500004-143



P500003-143



P350028-143

FINISH

- Graphite - 143

SEMI-FLUSH CONVERTIBLE

P350028-143 Graphite
Hanging and ceiling mount hardware included.
17-1/4" dia., 10-1/4" ht.
Overall ht. w/chain 72"; wire 10'.
Three medium base lamps, each 100w max.

MINI-PENDANT

P500003-143 Graphite
9-1/8" dia., 6-5/8" ht.
Overall ht. w/chain 72-1/2"; wire 10'.
One medium base lamp, 100w max.

SIX-LIGHT PENDANT

P500004-143 Graphite
25-1/4" dia., 20-5/8" ht.
Overall ht. w/chain 95-1/2"; wire 15'.
Six medium base lamps, each 100w max.

WALL SCONCE

P710001-143 Graphite
12" W., 5-5/8" ht.
Extends 6-1/8". H/CTR 2-5/8".
Two candelabra base lamps, each 60w max.



P710001-143



P500004-143

EVOKE

Evoke features an elliptical frame that gracefully supports a candelabra with clear glass shade. Mixed finishes highlight the unique shape and provide a hint of livable luxury to your home. Three-, five- and six-light options available.



P400117-020



P400024-020



P400026-020

FINISHES

- Antique Bronze - 020

THREE-LIGHT CHANDELIER

P400024-020 Antique Bronze
17-5/8" dia., 28-1/2" ht.
Overall ht. w/chain 103-1/2"; wire 15'.
Three candelabra base lamps,
each 60w max.

FIVE-LIGHT CHANDELIER

P400025-020 Antique Bronze
24-5/8" dia., 35-3/8" ht.
Overall ht. w/chain 110-1/2"; wire 15'.
Five candelabra base lamps,
each 60w max.

SIX-LIGHT CHANDELIER

P400026-020 Antique Bronze
28-1/2" dia., 39-1/2" ht.
Overall ht. w/chain 114-1/2"; wire 15'.
Six candelabra base lamps,
each 60w max.

FIVE-LIGHT CHANDELIER

P400117-020 Antique Bronze
33-3/4" dia., 27-7/8" ht.
Overall ht. w/chain 103"; wire 15'.
Five candelabra base lamps,
each 60w max.



P400024-020



P400117-020



*Fixtures shown with P7826-01
vintage lamps.*

N New Product



P400117-104

EVOKE



P400024-104



P400026-104

FINISHES

- Polished Nickel - 104

THREE-LIGHT CHANDELIER

P400024-104 Polished Nickel
17-5/8" dia., 28-1/2" ht.
Overall ht. w/chain 103-1/2"; wire 15'.
Three candelabra base lamps,
each 60w max.

FIVE-LIGHT CHANDELIER

P400025-104 Polished Nickel
24-5/8" dia., 35-3/8" ht.
Overall ht. w/chain 110-1/2"; wire 15'.
Five candelabra base lamps,
each 60w max.

SIX-LIGHT CHANDELIER

P400026-104 Polished Nickel
28-1/2" dia., 39-1/2" ht.
Overall ht. w/chain 114-1/2"; wire 15'.
Six candelabra base lamps,
each 60w max.

FIVE-LIGHT CHANDELIER

P400117-104 Polished Nickel
33-3/4" dia., 27-7/8" ht.
Overall ht. w/chain 103"; wire 15'.
Five candelabra base lamps,
each 60w max.

Fixtures shown with P7826-01
vintage lamps.



P400025-104



P400117-104

N

N New Product

DEBUT

Debut provides a fitting stage to feature nostalgic, vintage lamps. Glass accessory shades in clear or frosted seeded finishes are available to complement traditional incandescent or energy efficient lamps.



ALSO AVAILABLE IN

Bath & Vanity, page 206



P400015-009



P350036-009



P400015-009
shown with
P860003-001 shade

FINISH

● Brushed Nickel -009

WALL BRACKET

P300008-009 Brushed Nickel
4-1/2" W., 8-1/2" ht.
Extends 5-7/8". H/CTR 5".
One medium base lamp,
60w max.

SEMI-FLUSH CONVERTIBLE

P350036-009 Brushed Nickel
Hanging and ceiling mount
hardware included.
19-7/8" dia., 15" ht.
Overall ht. w/chain 52"; wire 10'.
Three medium base lamps,
each 60w max.

SIX-LIGHT CHANDELIER

P400015-009 Brushed Nickel
27-1/2" dia., 30" ht.
Overall ht. w/chain 102-1/2"; wire 15'.
Six medium base lamps,
each 60w max.

NINE-LIGHT CHANDELIER

P400016-009 Brushed Nickel
36" dia., 34-1/2" ht.
Overall ht. w/chain 109-1/2"; wire 15'.
Nine medium base lamps,
each 60w max.

FIFTEEN-LIGHT CHANDELIER

P400017-009 Brushed Nickel
36" dia., 41-5/8" ht.
Overall ht. w/chain 164-1/2"; wire 15'.
Fifteen medium base lamps,
each 60w max.

ACCESSORY SHADE

P860002-001 Frosted
seeded glass shade.
4-1/4" dia., 5-7/8" ht.

ACCESSORY SHADE

P860003-001 Clear
seeded glass shade.
4-1/4" dia., 5-7/8" ht.

*Fixtures shown with P7825-01
vintage lamps.*



P400017-009
shown with
P860002-001 shade



P300008-009



P300008-009
shown with
P860002-001 shade



P860002-001



P860003-001



P400016-009



DEBUT



P350036-143
shown with
P860002-001 shade



P400015-143



P400017-143
shown with
P860003-001 shade



P300008-143



P300008-143
shown with
P860003-001 shade



P400016-143



P860002-001



P860003-001

FINISH

● Graphite - 143

WALL BRACKET

P300008-143 Graphite
4-1/2" W., 8-1/2" ht.
Extends 5-7/8". H/CTR 5".
One medium base lamp,
60w max.

SEMI-FLUSH CONVERTIBLE

P350036-143 Graphite
Hanging and ceiling mount
hardware included.
19-7/8" dia., 15" ht.
Overall ht. w/chain 52"; wire 10'.
Three medium base lamps,
each 60w max.

SIX-LIGHT CHANDELIER

P400015-143 Graphite
27-1/2" dia., 30" ht.
Overall ht. w/chain 102-1/2"; wire 15'.
Six medium base lamps,
each 60w max.

NINE-LIGHT CHANDELIER

P400016-143 Graphite
36" dia., 34-1/2" ht.
Overall ht. w/chain 109-1/2"; wire 15'.
Nine medium base lamps,
each 60w max.

FIFTEEN-LIGHT CHANDELIER

P400017-143 Graphite
36" dia., 41-5/8" ht.
Overall ht. w/chain 164-1/2"; wire 15'.
Fifteen medium base lamps,
each 60w max.

ACCESSORY SHADE

P860002-001 Frosted
seeded glass shade.
4-1/4" dia., 5-7/8" ht.

ACCESSORY SHADE

P860003-001 Clear
seeded glass shade.
4-1/4" dia., 5-7/8" ht.

*Fixtures shown with P7825-01
vintage lamps.*

ASPEN CREEK

Fixtures within the Aspen Creek collection offer a handsome look for farmhouse or rustic living spaces. Featuring a steel design frame painted to emulate driftwood, a Brushed Nickel finish adds a modern element. Etched natural parchment glass shades complete the look.



P400027-009



P400027-009



P500020-009

FINISH

● Brushed Nickel - 009

SEMI-FLUSH CONVERTIBLE

P350041-009 Brushed Nickel
Hanging and ceiling mount hardware included.
14-1/8" dia., 11" ht.
Overall ht. w/chain 51"; wire 10'.
Two medium base lamps, each 75w max.

FOUR-LIGHT CHANDELIER

P400027-009 Brushed Nickel
25" dia., 23" ht.
Overall ht. w/chain 95"; wire 15'.
Four medium base lamps, each 100w max.

FIVE-LIGHT CHANDELIER

P400028-009 Brushed Nickel
30" dia., 24" ht.
Overall ht. w/chain 96"; wire 15'.
Five medium base lamps, each 100w max.



P350041-009

MINI-PENDANT

P500020-009 Brushed Nickel
6-5/8" dia., 9-1/4" ht.
Overall ht. w/stem 75-1/2"; wire 10'.
One medium base lamp, 100w max.

WALL BRACKET

P710008-009 Brushed Nickel
4-3/4" W., 12-3/8" ht.
Extends 5-3/4". H/CTR 5-3/4".
One medium base lamp, 100w max.




P400028-009



P710008-009

REMIX

Remix features industrial-inspired pendant options. A Graphite frame is comprised of straps that weave together to create an open cage design. Brushed Nickel accents on the inside add a touch of mixed metal accents.



P500012-143

P500010-143



P400051-143



FINISH

● Graphite - 143

FIVE-LIGHT CHANDELIER

P400051-143 Graphite
26" dia., 20" ht. Overall ht. w/stem 86", wire 15'.
Five medium base lamps, each 60w max.

MINI-PENDANT

P500010-143 Graphite
10" dia., 9-1/4" ht.
Overall ht. w/stem 75-1/2"; wire 10'.
One medium base lamp, 60w max.

THREE-LIGHT PENDANT

P500011-143 Graphite
16" dia., 15" ht.
Overall ht. w/stem 81"; wire 15'.
Three medium base lamps, each 60w max.

FOUR-LIGHT PENDANT

P500012-143 Graphite
22" dia., 15" ht.
Overall ht. w/stem 81"; wire 15'.
Four medium base lamps, each 60w max.

P500011-143



P500012-143



Fixtures shown with P7825-01 vintage lamps

 New Product

FONTAYNE NEW

With updated designs that honor the charm of early American styling, Fontayne provides a timeless elegance to Rustic Farmhouse, Modern Farmhouse and Urban Industrial spaces. Impressive graphic elements take center stage, while candelabra lights highlight subtle curves. Dual tone finish combinations include Antique Bronze with faux oak accents or Brushed Nickel with weathered gray accents.



P400080-020

P400080-020



P500088-020



FINISHES

- Antique Bronze - 020

FOUR-LIGHT CHANDELIER

P400080-020 Antique Bronze
15-3/4" dia., 30" ht.
Overall ht. w/chain 105", wire 15'.
Four candelabra base lamps,
each 60w max.

SIX-LIGHT CHANDELIER

P400081-020 Antique Bronze
22" dia., 24-3/4" ht.
Overall ht. w/chain 111-1/2", wire 15'.
Six candelabra base lamps,
each 60w max.

P400081-020



P500089-020



SIX-LIGHT LINEAR CHANDELIER

P400082-020 Antique Bronze
36" W., 22" L., 15-3/4" ht.
Overall ht. w/chain 103-1/2", wire 15'.
Six candelabra base lamps,
each 60w max.

TWELVE-LIGHT CHANDELIER

P400083-020 Antique Bronze
32" dia., 28-3/4" ht.
Overall ht. w/chain 107", wire 15'.
Twelve candelabra base lamps,
each 60w max.

FOUR-LIGHT PENDANT

P500088-020 Antique Bronze
14" Sq., 25" ht.
Overall ht. w/chain 99", wire 15'.
Four candelabra base lamps,
each 60w max.

P400083-020



P400082-020



SIX-LIGHT PENDANT

P500089-020 Antique Bronze
20" Sq., 32" ht.
Overall ht. w/chain 107-1/2", wire 15'.
Six candelabra base lamps,
each 60w max.

Fixtures shown with P7826-01 vintage lamps



P400080-009

NEW

FONTAYNE

P400080-009



P500088-009



FINISHES

- Brushed Nickel - 009

FOUR-LIGHT CHANDELIER

P400080-009 Brushed Nickel
15-3/4" dia., 30" ht.
Overall ht. w/chain 105", wire 15'.
Four candelabra base lamps,
each 60w max.

SIX-LIGHT CHANDELIER

P400081-009 Brushed Nickel
22" dia., 24-3/4" ht.
Overall ht. w/chain 111-1/2", wire 15'.
Six candelabra base lamps,
each 60w max.

P400081-009



P500089-009



SIX-LIGHT LINEAR CHANDELIER

P400082-009 Brushed Nickel
36" W., 22" L., 15-3/4" ht.
Overall ht. w/chain 103-1/2", wire 15'.
Six candelabra base lamps,
each 60w max.

TWELVE-LIGHT CHANDELIER

P400083-009 Brushed Nickel
32" dia., 28-3/4" ht.
Overall ht. w/chain 107", wire 15'.
Twelve candelabra base lamps,
each 60w max.

FOUR-LIGHT PENDANT

P500088-009 Brushed Nickel
14" Sq., 25" ht.
Overall ht. w/chain 99", wire 15'.
Four candelabra base lamps,
each 60w max.

P400083-009



P400082-009



SIX-LIGHT PENDANT

P500089-009 Brushed Nickel
20" Sq., 32" ht.
Overall ht. w/chain 107-1/2", wire 15'.
Six candelabra base lamps,
each 60w max.

*Fixtures shown with P7826-01
vintage lamps*

TURNBURY

Coastal-inspired pieces are popular in a variety of today's home designs. Turnbury pendants feature a solid wood frame surround with hand-painted, galvanized metal fittings. The distressed pine frame finish is reminiscent of driftwood that has been weathered in the sun.



P4761-141



P5317-141
Shown with
P7825-01
vintage lamps



P4760-141

FINISH

- Galvanized Finish - 141

FOUR-LIGHT CHANDELIER

P4760-141 Galvanized Finish
16" dia., 18-3/4" ht.
Overall ht. w/chain 93-1/2", wire 15'.
Four candelabra base lamps
each, 60w max.

SIX-LIGHT CHANDELIER

P4761-141 Galvanized Finish
26" dia., 28-3/4" ht.
Overall ht. w/chain 103-1/2", wire 15'.
Six candelabra base lamps
each, 60w max.

EIGHT-LIGHT CHANDELIER

P4763-141 Galvanized Finish
Two tier
36" W., 39" ht.
Overall ht. w/chain 162", wire 15'.
Eight candelabra base lamps,
each 60w max.

ONE-LIGHT MINI-PENDANT

P5317-141 Galvanized Finish
10" dia., 12-1/4" ht.
Overall ht. w/chain 87", wire 10'.
One medium base lamp,
100w max.

*Fixtures shown with P7826-01
vintage lamps unless noted*



P4761-141

N

N New Product

SPICEWOOD

The statement-making Spicewood pendants feature a rich, solid wood surround in a classic quatrefoil pattern. Wrought iron metal fittings in a Gilded Iron finish are paired with a distressed pine frame to complement rustic and reclaimed design styles.



P4766-71



P5318-71
shown with
P7825-01
vintage lamp



P4766-71

FINISH

- Gilded Iron - 71

FOUR-LIGHT CHANDELIER

P4766-71 Gilded Iron
22" dia., 24-1/2" ht.
Overall ht. w/chain 99-1/2", wire 15'.
Four candelabra base lamps
each, 60w max.

SIX-LIGHT CHANDELIER

P4767-71 Gilded Iron
30" dia., 32-1/2" ht.
Overall ht. w/chain 107-1/2", wire 15'.
Six candelabra base lamps
each, 60w max.

ONE-LIGHT MINI-PENDANT

P5318-71 Gilded Iron
10" dia., 11" ht.
Overall ht. w/stem 77", wire 10'.
One medium base lamp,
100w max.

*Fixtures shown with P7826-01
vintage lamps unless noted*



P4767-71

SOIREE

Featuring a handsome, repeating geometric pattern and an updated iron frame, Soiree offers a touch of sparkle to any room. The glass shades in the bath, mini pendant and chandelier fixtures are secured with a locking ring – offering form and function for each fixture within the collection.



ALSO AVAILABLE IN
Bath & Vanity, page 200



P400037-020



FINISH

- Antique Bronze - 020

ONE-LIGHT WALL BRACKET

P300035-020 Antique Bronze
4-3/4" W., 21" ht.
Extends 6". H/CTR 8-5/8".
One candelabra base lamp,
60w max.

SEMI-FLUSH CONVERTIBLE

P350050-020 Antique Bronze
Hanging and ceiling mount
hardware included.
15" dia., 12" ht.
Overall ht. w/chain 51"; wire 10'.
Three candelabra base lamps,
each 60w max.

THREE-LIGHT CHANDELIER

P400018-020 Antique Bronze
22" dia., 21-7/8" ht.
Overall ht. w/chain 97"; wire 15'.
Three candelabra base lamps,
each 60w max.

FIVE-LIGHT CHANDELIER

P400037-020 Antique Bronze
25-5/8" dia., 26-1/2" ht.
Overall ht. w/chain 101-1/2"; wire 15'.
Five candelabra base lamps,
each 60w max.

NINE-LIGHT CHANDELIER

P400038-020 Antique Bronze
34-1/4" dia., 38" ht.
Overall ht. w/chain 161"; wire 15'.
Nine candelabra base lamps,
each 60w max.

MINI-PENDANT

P500024-020 Antique Bronze
5-5/8" dia., 17-7/8" ht.
Overall ht. w/stem 83"; wire 10'.
One candelabra base lamp,
60w max.

*Fixtures shown with P7826-01
vintage lamps*

NOMA

Mixed finishes, such as Polished Nickel with silver ridge accents and Antique Bronze with champagne accents are highlighted in Noma. Soft angles and curving lines created from flat metal straps elegantly frame etched white glass shades.



P400012-020



FINISH

● Antique Bronze - 020

SEMI-FLUSH CONVERTIBLE

P350034-020 Antique Bronze
Hanging and ceiling mount hardware included.
15-5/8" dia., 12-1/2" ht.
Overall ht. w/chain 51-1/2"; wire 10'.
Two medium base lamps, each 100w max.

THREE-LIGHT CHANDELIER

P400011-020 Antique Bronze
23" dia., 17-7/8" ht.
Overall ht. w/chain 92-1/2"; wire 15'.
Three medium base lamps, each 100w max.

FIVE-LIGHT CHANDELIER

P400012-020 Antique Bronze
28-1/2" dia., 26" ht.
Overall ht. w/chain 101"; wire 15'.
Five medium base lamps, each 100w max.

NINE-LIGHT CHANDELIER

P400013-020 Antique Bronze
Two-tier.
34" dia., 32" ht.
Overall ht. w/chain 155"; wire 15'.
Nine medium base lamps, each 100w max.

FOUR-LIGHT FOYER PENDANT

P400014-020 Antique Bronze
16" dia., 29-1/4" ht.
Overall ht. w/chain 104"; wire 15'.
Four candelabra base lamps, each 60w max.

MINI-PENDANT

P500007-020 Antique Bronze
7-3/8" dia., 6-1/2" ht.
Overall ht. w/stem 72-1/2"; wire 10'.
One medium base lamp, 100w max.

WALL BRACKET

P710005-020 Antique Bronze
7-3/8" W., 18-5/8" ht.
Extends 8-3/8". H/CTR 6-3/4".
One medium base lamp, 100w max.



NOMA



P350034-104



P400011-104



P400012-104



P400013-104



P500007-104



P710005-104

FINISH

- Polished Nickel - 104

SEMI-FLUSH CONVERTIBLE

P350034-104 Polished Nickel
Hanging and ceiling mount hardware included.
15-5/8" dia., 12-1/2" ht.
Overall ht. w/chain 51-1/2"; wire 10'.
Two medium base lamps, each 100w max.

THREE-LIGHT CHANDELIER

P400011-104 Polished Nickel
23" dia., 17-7/8" ht.
Overall ht. w/chain 92-1/2"; wire 15'.
Three medium base lamps, each 100w max.

FIVE-LIGHT CHANDELIER

P400012-104 Polished Nickel
28-1/2" dia., 26" ht.
Overall ht. w/chain 101"; wire 15'.
Five medium base lamps, each 100w max.

NINE-LIGHT CHANDELIER

P400013-104 Polished Nickel
Two-tier.
34" dia., 32" ht.
Overall ht. w/chain 155"; wire 15'.
Nine medium base lamps, each 100w max.

FOUR-LIGHT FOYER PENDANT

P400014-104 Polished Nickel
16" dia., 29-1/4" ht.
Overall ht. w/chain 104"; wire 15'.
Four candelabra base lamps, each 60w max.

MINI-PENDANT

P500007-104 Polished Nickel
7-3/8" dia., 6-1/2" ht.
Overall ht. w/stem 72-1/2"; wire 10'.
One medium base lamp, 100w max.

WALL BRACKET

P710005-104 Polished Nickel
7-3/8" W., 18-5/8" ht.
Extends 8-3/8". H/CTR 6-3/4".
One medium base lamp, 100w max.

MARCHÉ NEW

Marché is an eclectic arrangement of gleaming metal turnings, which recreates the vintage styles found in Parisian neighborhood markets. Polished Nickel elements are combined with a luxurious sheer silver organza shade and clear K9 glass elements. Coordinate with Nissé or Caress collections to create a truly distinctive addition to your home.



P400049-104



P400049-104



P710013-104

FINISH

● Polished Nickel - 104

SEMI-FLUSH CONVERTIBLE

P350029-104 Polished Nickel
Hanging and ceiling mount hardware included.
18" dia., 14" ht.
Overall ht. w/chain 55", wire 10'.
Three candelabra base lamps, each 60w max.

FIVE-LIGHT CHANDELIER

P400049-104 Polished Nickel
28" dia., 25-1/8" ht.
Overall ht. w/chain 100", wire 15'.
Five candelabra base lamps, each 60w max.

FOUR-LIGHT PENDANT

P500043-104 Polished Nickel
22" dia., 20" ht.
Overall ht. w/chain 95", wire 15'.
Four candelabra base lamps, each 60w max.

WALL BRACKET

P710013-104 Polished Nickel
6-7/8" W., 12-1/4" ht.
Extends 10-1/2". H/CTR 6-5/8".
One candelabra base lamp, 60w max.



P500043-104



P350029-104

SAVOR NEW

Savor is a soft blend of sweeping details and contemporized wrought iron craftsmanship making it suitable for a wide variety of home décor styles. Sheer sailcloth textured shades are integral to the design.



P400075-134



P350092-134



P500080-134

FINISH

- Silver Ridge - 134

SEMI-FLUSH CONVERTIBLE

P350092-134 Silver Ridge Hanging and ceiling mount hardware included. 17" dia., 15-1/2" ht. Overall ht. w/chain 56-1/2", wire 10'. Four candelabra base lamps, each 60w max.

SIX-LIGHT CHANDELIER

P400075-134 Silver Ridge 33" dia., 27-1/2" ht. Overall ht. w/chain 102-1/2", wire 15'. Six candelabra base lamps, each 60w max.



P500081-134



P400075-134

TEN-LIGHT CHANDELIER

P400076-134 Silver Ridge 38" dia., 35-3/4" ht. Overall ht. w/chain 159", wire 15'. Ten candelabra base lamps, each 60w max.

MINI-PENDANT

P500080-134 Silver Ridge 10" dia., 14-1/2" ht. Overall ht. w/stem 80-1/2", wire 10'. One medium base lamp, 100w max.

SIX-LIGHT PENDANT

P500081-134 Silver Ridge 24" dia., 25-1/4" ht. Overall ht. w/chain 100-1/2", wire 15'. Six candelabra base lamps, each 60w max.



P710029-134



P400076-134

WALL BRACKET

P710029-134 Silver Ridge 6-5/8" W., 18" ht. Extends 8". H/CTR 9". One candelabra base lamp, 60w max.

WEST VILLAGE

A modern form with industrial-inspired accents are featured in West Village. Double prismatic glass shades provide a beautiful illumination effect. Visual interest continues with a three-spoke frame that holds each glass shade. Antique Bronze with antique brass accents or Brushed Nickel with chrome accents provide touches of mixed metal in all fixtures within the collection.



ALSO AVAILABLE IN
Bath & Vanity, page 212



P400009-020



P400008-020



P500006-020

FINISHES

- Antique Bronze - 20

WALL BRACKET

P300004-020 Antique Bronze
5-1/8" W., 8-1/8" ht.
Extends 7". H/CTR 4-1/8".
One medium base lamp,
100w max.

SEMI-FLUSH CONVERTIBLE

P350032-020 Antique Bronze
Hanging and ceiling mount
hardware included.
13-1/2" dia., 9-1/4" ht.
Overall ht. w/stem 75"; wire 15'.
One medium base lamp,
100w max.

THREE-LIGHT CHANDELIER

P400008-020 Antique Bronze
20" dia., 16-1/8" ht.
Overall ht. w/stem 82-1/2"; wire 15'.
Three medium base lamps,
each 100w max.



P300004-020

FIVE-LIGHT CHANDELIER

P400009-020 Antique Bronze
25" dia., 20-1/8" ht.
Overall ht. w/stem 86-1/2"; wire 15'.
Five medium base lamps,
each 100w max.

NINE-LIGHT CHANDELIER

P400010-020 Antique Bronze
31-1/4" dia., 20-3/8" ht.
Overall ht. w/stem 86-1/2"; wire 15'.
Nine medium base lamps,
each 100w max.



P400010-020

MINI-PENDANT

P500006-020 Antique Bronze
5-1/8" dia., 7-5/8" ht.
Overall ht. w/stem 74"; wire 10'.
One medium base lamp,
100w max.



P350032-020



P350032-020



P400009-009

WEST VILLAGE



FINISHES

- Brushed Nickel - 009

WALL BRACKET

P300004-009 Brushed Nickel
5-1/8" W., 8-1/8" ht.
Extends 7". H/CTR 4-1/8".
One medium base lamp,
100w max.

SEMI-FLUSH CONVERTIBLE

P350032-009 Brushed Nickel
Hanging and ceiling mount
hardware included.
13-1/2" dia., 9-1/4" ht.
Overall ht. w/stem 75"; wire 15'.
One medium base lamp,
100w max.

THREE-LIGHT CHANDELIER

P400008-009 Brushed Nickel
20" dia., 16-1/8" ht.
Overall ht. w/stem 82-1/2"; wire 15'.
Three medium base lamps,
each 100w max.



FIVE-LIGHT CHANDELIER

P400009-009 Brushed Nickel
25" dia., 20-1/8" ht.
Overall ht. w/stem 86-1/2"; wire 15'.
Five medium base lamps,
each 100w max.



NINE-LIGHT CHANDELIER

P400010-009 Brushed Nickel
31-1/4" dia., 20-3/8" ht.
Overall ht. w/stem 86-1/2"; wire 15'.
Nine medium base lamps,
each 100w max.

MINI-PENDANT

P500006-009 Brushed Nickel
5-1/8" dia., 7-5/8" ht.
Overall ht. w/stem 74"; wire 10'.
One medium base lamp,
100w max.



METRIC NEW

The Metric collection embodies a modern spirit with square etched opal glass shades that are set inside a die-cast holder. The sleek frame provides an architectural support that is elegant both in its simplicity and artful craftsmanship. Polished Chrome or Brushed Nickel finishes are the perfect complement to the contemporary design.



ALSO AVAILABLE IN
Bath & Vanity, page 226



P400045-009



P350021-009



P350021-015

FINISHES

- Brushed Nickel - 009
- Polished Chrome - 015

TWO-LIGHT SEMI-FLUSH

P350021-009 Brushed Nickel
P350021-015 Polished Chrome
 16" W., 4-1/2" L., 12-1/2" ht.
 Two medium base lamps,
 each 100w max.



P400045-009



P400045-015

FOUR-LIGHT CHANDELIER

P400045-009 Brushed Nickel
P400045-015 Polished Chrome
 24" W., 13-1/4" ht. Overall ht. w/
 stem 70-1/2", wire 15'.
 Four medium base lamps,
 each 100w max.



P400046-009



P400046-015

SIX-LIGHT CHANDELIER

P400046-009 Brushed Nickel
P400046-015 Polished Chrome
 26" W., 13-1/4" ht. Overall ht. w/
 stem 70-1/2", wire 15'.
 Six medium base lamps,
 each 100w max.

CORDIN NEW

Featuring a striking combination of traditional and modern design, classic styling in the Cordin collection highlights a distinctive look for a variety of interiors. Elegant linear arms and a double-lined linen shade create a softer feel when combined with the vintage mechanical details and dual-tone frame. A Brushed Nickel finish with natural brass accents are incorporated in all fixtures in the Cordin family, including chandeliers, semi-flush, mini-pendant, island and swing arm options.



P400090-009



P710034-009



P400089-009



P500101-009



P400092-009



P350095-009



P400091-009

FINISH

- Brushed Nickel - 009

SEMI-FLUSH CONVERTIBLE

P350095-009 Brushed Nickel
Hanging and ceiling mount hardware included.
16" dia., 12-1/2" ht.
Overall ht. w/stem 78", wire 10'.
Three medium base lamps, each 60w max.

THREE-LIGHT CHANDELIER

P400089-009 Brushed Nickel
25" dia., 19" ht.
Overall ht. w/stem 85", wire 15'.
Three medium base lamps, each 75w max.

FIVE-LIGHT CHANDELIER

P400090-009 Brushed Nickel
30" dia., 20" ht.
Overall ht. w/stem 86", wire 15'.
Five medium base lamps, each 75w max.

NINE-LIGHT CHANDELIER

P400091-009 Brushed Nickel
38" dia., 26" ht.
Overall ht. w/stem 92", wire 180.
Nine medium base lamps, each 75w max.

THREE-LIGHT LINEAR CHANDELIER

P400092-009 Brushed Nickel
38" W., 10" L., 21" ht.
Overall ht. w/stem 87", wire 15'.
Three medium base lamps, each 75w max.

MINI-PENDANT

P500101-009 Brushed Nickel
10" dia., 8" ht.
Overall ht. w/stem 74", wire 10'.
One medium base lamp, 75w max.

WALL BRACKET

P710034-009 Brushed Nickel
10" W., 17-1/2" ht.
Extends 13-1/2". H/CTR 13-1/8".
Arm pivots 120°
One medium base lamp, 75w max.

ASSEMBLY HALL

Assembly Hall provides a formal and classic open caged pendant for a variety of traditional and transitional interiors. Available in two sizes, arching frames are great in scale and surround a candelabra with matching candles – Antique Bronze fixtures also include vintage brass candles for additional customization.



P500036-020



FINISHES

- Brushed Nickel - 009
- Antique Bronze - 020

FOUR-LIGHT FOYER PENDANT

P500036-009 Brushed Nickel
P500036-020 Antique Bronze
 15" sq., 26" ht.
 Overall ht. w/chain 100"; wire 15'.
 Four candelabra base lamps,
 each 60w max.

SIX-LIGHT FOYER PENDANT

P500037-009 Brushed Nickel
P500037-020 Antique Bronze
 20" sq., 32-3/4" ht.
 Overall ht. w/chain 106-1/2"; wire 15'.
 Six candelabra base lamps,
 each 60w max.



**EIGHT-LIGHT FOYER
PENDANT**

P500097-009 Brushed Nickel
P500097-020 Antique Bronze
 25" Sq., 39-5/8" ht.
 Overall ht. w/chain 106-1/2", wire 15'.
 Eight candelabra base lamps,
 each 60w max.

*Note: Antique Bronze fixtures
include Vintage Brass and
Antique Bronze candle covers
for additional customization.*

*Fixtures shown with P7826-01
vintage lamps*



N New Product

WESTFALL NEW

Westfall is a combination of arching elements that create a dramatic soaring frame. A dual-tone finish highlights the distinctive form. Metal fittings add a touch of elegance and dimension to further enhance the classic architectural form.



P500040-143



FINISHES

- Antique Bronze - 020
- Graphite - 143

FOUR-LIGHT FOYER PENDANT

P500038-020 Antique Bronze
P500038-143 Graphite
 10-1/8" sq., 19-5/8" ht. Overall ht. w/
 chain 94-1/2", wire 15'.
 Four candelabra base lamps,
 each 60w max.



FOUR-LIGHT FOYER PENDANT

P500039-020 Antique Bronze
P500039-143 Graphite
 13-7/8" sq., 25-1/8" ht. Overall ht. w/
 chain 100", wire 15'.
 Four candelabra base lamps,
 each 60w max.

**EIGHT-LIGHT FOYER
 PENDANT**

P500040-020 Antique Bronze
P500040-143 Graphite
 two-tier.
 19-3/4" sq., 33-1/8" ht. Overall ht.
 w/chain 156", wire 15'.
 Eight candelabra base lamps,
 each 60w max.

*Note: Antique Bronze fixtures
 include Vintage Brass and
 Antique Bronze candle covers
 for additional customization.*

*Fixtures shown with P7826-01
 vintage lamps*



CAPTIVATE NEW

The Captivate collection features a striking circular frame that surrounds arching candelabra. Glazed with clear seeded glass, the artful form is a complex layering of light and shadow to provide a dramatic focal point to any room. The Graphite finish provides a rich, smoky color palette to complement your décor.



P500049-143



P500049-143

FINISH

● Graphite - 143

FOUR-LIGHT PENDANT

P500048-143 Graphite
18" Sq. dia., 17-1/2" ht.
Overall ht. w/stem 83-1/2", wire 10'.
Four candelabra base lamps,
each 60w max.

EIGHT-LIGHT PENDANT

P500049-143 Graphite
24" Sq. dia., 23-1/8" ht.
Overall ht. w/stem 89", wire 10'.
Eight candelabra base lamps,
each 60w max.

WALL SCONCE

P710021-143 Graphite
10" W., 10" ht.
Extends 5-1/2". H/CTR 5".
One candelabra base lamp,
60w max.

*Fixtures shown with P7826-01
vintage lamps*



P500048-143



P710021-143

LOOKING GLASS NEW

Whether for a mountain cabin or an urban retreat, the rustic charm of the Looking Glass collection is an artful display of romantic vintage lighting. Inspired by a timber frame farmhouse, Looking Glass features iron elements that support clear seeded glass reflectors. Hints of brass accentuate the mechanical details to enhance a vintage feel.



P400002-020



FINISH

● Antique Bronze - 020

FOUR-LIGHT CHANDELIER

P400002-020 Antique Bronze
25-3/8" W., 18-1/4" ht.
Overall ht. w/stem 84", wire 15'.
Four medium base lamps,
each 60w max.

SIX-LIGHT CHANDELIER

P400003-020 Antique Bronze
19" W., 36-3/4" L., 18-1/4" ht.
Overall ht. w/stem 84", wire 15'.
Six medium base lamps,
each 60w max.

MINI-PENDANT

P500042-020 Antique Bronze
9" dia., 14 3/4" ht.
Overall ht. w/stem 81", wire 10'.
One medium base lamp,
100w max.

WALL SCONCE

P710002-020 Antique Bronze
9" W., 17-7/8" ht.
Extends 7-5/8". H/CTR 11-3/8".
One medium base lamp,
60w max.

*Fixtures shown with P7825-01
vintage lamps*



MARQUE

With antique textured glass in an Antique Bronze frame and clear water glass in the Graphite finish, this vintage pendant family can be used as a sleek substitute for chandeliers in a variety of living spaces, including foyers and hallways.



P3598-143

FINISHES

- Antique Bronze - 20
- Graphite - 143

ONE-LIGHT FOYER

P3598-20 Antique Bronze
P3598-143 Graphite
 12" dia., 19-3/4" ht.
 Overall ht. w/stem 86"; wire 15'.
 One medium base lamp,
 100w max.

THREE-LIGHT FOYER

P3601-20 Antique Bronze
P3601-143 Graphite
 18" dia., 28-3/4" ht.
 Overall ht. w/stem 95"; wire 15'.
 Three medium base lamps,
 each 100w max.

MINI-PENDANT

P5073-20 Antique Bronze
P5073-143 Graphite
 7-3/4" dia., 9-1/4" ht.
 Overall ht. w/stem 75-1/4"; wire 10'.
 One medium base lamp,
 100w max.

*Fixtures shown with P7825-01
 vintage lamps*



WEMBERLY

Appreciate handcraftsmanship and organic modern forms in Wemberly. The Graphite frame is hand crafted and softened with a white linen shade. Mini pendant, semi-flush, linear and wall bracket options are available.



P500017-143



P500017-143

FINISH

- Graphite - 143

SEMI-FLUSH CONVERTIBLE

P350027-143 Graphite
Hanging and ceiling mount hardware included.
16" dia., 13-1/8" ht.
Overall ht. w/stem 77"; wire 10'.
Three medium base lamps, each 100w max.

MINI-PENDANT

P500016-143 Graphite
6-3/8" dia., 8-1/2" ht.
Overall ht. w/stem 74-1/2"; wire 10'.
One medium base lamp, 100w max.

FOUR-LIGHT PENDANT

P500017-143 Graphite
32" L., 14" W., 9-1/2" ht.
Overall ht. w/stem 75-1/2"; wire 15'.
Four medium base lamps, each 100w max.

WALL BRACKET

P710007-143 Graphite
6-3/8" W., 9-1/8" ht.
Extends 8-1/4". H/CTR 4-3/4".
One medium base lamp, 100w max.



P350027-143



P710007-143



P500016-143

RATIO

A sleek metal frame supports a low-slung shade to create Ratio's casual modern style. The frame's proportion to the white linen drum shade evokes a perfect ratio for lighting. All fixtures include a polished glass diffuser that offers an elegant appeal.



P5015-20



P3604-09
shown as
pendant



P3604-09
shown as semi-flush

FINISHES

- Brushed Nickel - 09
- Antique Bronze - 20

SEMI-FLUSH CONVERTIBLE

P3604-09 Brushed Nickel
P3604-20 Antique Bronze
 Hanging and ceiling mount hardware included.
 16" dia., 11-1/2" ht.
 Overall ht. w/stem 77-1/2", wire 10'.
 Three medium base lamps, each 75w max.

FOUR-LIGHT PENDANT

P5015-09 Brushed Nickel
P5015-20 Antique Bronze
 Hanging and ceiling mount hardware included.
 24" dia., 15-7/8" ht.
 Overall ht. w/stem 82", wire 10'.
 Four medium base lamps, each 75w max.

SIX-LIGHT PENDANT

P5021-09 Brushed Nickel
P5021-20 Antique Bronze
 Hanging and ceiling mount hardware included.
 30" dia., 19-1/8" ht.
 Overall ht. w/stem 85", wire 10'.
 Six medium base lamps, each 75w max.



P5015-09



P5021-09



P3604-20



P5021-20

CINQ

Cinq finds inspiration from modern geometric designs and the beauty of contrasting elements. Five-sided bottom panels feature antique mirrored glass, while the upper panels are comprised of clear glass. Flush mount and pendant options are finished in an Antique Bronze.



P5322-20



P5319-20



P5322-20



P3868-20

FINISHES

- Antique Bronze - 20

ONE-LIGHT PENDANT

P5319-20 Antique Bronze
12" dia., 18-1/2" ht.
Overall ht. w/stem 84-1/2"
One medium base lamp,
100w max.

THREE-LIGHT PENDANT

P5322-20 Antique Bronze
19" dia., 25-7/8" ht.
Overall ht. w/stem 92"; wire 10'.
Three medium base lamps,
each 100w max.

ONE-LIGHT FLUSH MOUNT

P3868-20 Antique Bronze
12" dia., 9-1/4" ht.
One medium base lamp,
100w max.

*Fixtures shown with P7825-01
vintage lamps*

BEAKER

Beaker has a heightened sense of modern industrial styling. Available in two styles, each with their own unique character. These vessels are suspended from herringbone cloth cords. Available in two finishes, half clear, half mirrored glass with Polished Chrome frame or champagne glass with Antique Bronze frame.



P5344-1530K9



FINISHES

- Polished Chrome - 15
- Antique Bronze - 20

ONE-LIGHT LED MINI-PENDANT

P5344-1530K9 Polished Chrome
 5" dia., 11-7/8" ht.
 Overall ht. w/chain 122"; cord 10'.
 One 3000K 9w LED module included,
 623 source lumens, 90 CRI.



ONE-LIGHT LED MINI-PENDANT

P5345-2030K9 Antique Bronze
 10-1/4" dia., 11-1/2" ht.
 Overall ht. w/chain 121-1/2"; cord 10'.
 One 3000K 9w LED module included,
 623 source lumens, 90 CRI.



ONE-LIGHT LED WALL BRACKET

P7117-1530K9 Polished Chrome
 4-3/4" W., 17" ht.
 Extends 9-1/8". H/CTR 4".
 One 3000K 9w LED module included,
 623 source lumens, 90 CRI.



ONE-LIGHT LED WALL BRACKET

P7125-2030K9 Antique Bronze
 10-1/4" W., 16-5/8" ht.
 Extends 11-7/8". H/CTR 4".
 One 3000K 9w LED module included,
 623 source lumens, 90 CRI.



OVERBROOK

Overbrook features a scrolling frame surrounding a sailcloth textured shade in a Natural Linen finish. Available in an Antique Bronze or a Silver Ridge finish.



P5336-20



FINISHES

- Antique Bronze - 20
- Silver Ridge - 134

THREE-LIGHT PENDANT

P5335-20 Antique Bronze
P5335-134 Silver Ridge
 22" dia., 18-5/8" ht.
 Overall ht. w/stem 84", wire 15'.
 Three medium base lamps
 each 75w max.

FOUR-LIGHT PENDANT

P5336-20 Antique Bronze
P5336-134 Silver Ridge
 28" dia., 23-3/4" ht.
 Overall ht. w/stem 89", wire 15'.
 Four medium base lamps
 each 75w max.



ELLYSON

NEW

Clear prismatic glass creates a sophisticated, spherical globe in Ellyson. Influenced by mid century aesthetics, the glass is highlighted by simple accents finished in Polished Chrome or Brushed Bronze. From Mid-Century Modern to Luxe and Vintage Electric to Coastal, these pendants enhance a variety of design styles and can be displayed singularly or in groupings of two or more.



P500118-109



FINISHES

- Polished Chrome - 015
- Brushed Bronze - 109

ONE-LIGHT PENDANT

P500118-015 Polished Chrome
P500118-109 Brushed Bronze
 18-3/8" dia., 24" ht.
 Overall ht. w/stem 90", wire 10'.
 One medium base lamp,
 100w max.

GALLEY

Galley is a simple modern form that complements both coastal décor and commercial style kitchens. The arched supporting frame features overscale metal turnings for an enhanced sense of architectural styling. The linen shades are comprised of rich, satin lining for the feel of a tailored fit and finish to complement the multi-light cluster.



P500047-020



FINISHES


- Antique Bronze - 020
- Polished Nickel - 104

TWO-LIGHT PENDANT

P500046-020 Antique Bronze
P500046-104 Polished Nickel
 15" dia., 18" ht. Overall ht. w/stem
 84", wire 10'.
 Two medium base lamps,
 each 75w max.

THREE-LIGHT PENDANT

P500047-020 Antique Bronze
P500047-104 Polished Nickel
 21" dia., 24-1/2" ht. Overall ht. w/
 stem 90-1/2, wire 10'.
 Three medium base lamps,
 each 75w max.



Detail of pendant interior

MOBI

Mobi strikes a dramatic note for modern spaces. Suspended by steel cables, the etched glass shade is encased in an open frame finished in Graphite.



P500026-143



FINISH

- Graphite - 143

ONE-LIGHT PENDANT

P500025-143 Graphite
 12-7/8" dia., 36-1/2" ht.
 Overall ht. w/chain 97"; wire 10'.
 One medium base lamp,
 100w max.

ONE-LIGHT PENDANT

P500026-143 Graphite
 18-3/4" dia., 43-3/8" ht.
 Overall ht. w/chain 115"; wire 10'.
 One medium base lamp,
 100w max.

STAUNTON

Inspired by the stacked modern elements of items found in Parisian boutiques, Staunton's chess piece silhouette offers a signature focal point. Available in three shapes and color variations – they can be grouped as a single style or mixed and matched to offer a more eclectic look. All pendants feature a vintage, woven cloth cord.



P5332-20



FINISHES

- Brushed Nickel - 09
- Antique Bronze - 20
- Graphite - 143

ONE-LIGHT PENDANT

P5332-09 Brushed Nickel with clear glass
P5332-20 Antique Bronze with champagne glass
P5332-143 Graphite with smoked glass
 12" dia., 11-1/4" ht.
 Overall ht. w/cord 125-1/2"; cord 10'.
 One medium base lamp, 75w max.



ONE-LIGHT PENDANT

P5333-09 Brushed Nickel with clear glass
P5333-20 Antique Bronze with champagne glass
P5333-143 Graphite with smoked glass
 9" dia., 16-1/2" ht.
 Overall ht. w/cord 124"; cord 10'.
 One medium base lamp, 75w max.


ONE-LIGHT PENDANT

P5334-09 Brushed Nickel with clear glass
P5334-20 Antique Bronze with champagne glass
P5334-143 Graphite with smoked glass
 8 1/2" dia., 12-3/4" ht.
 Overall ht. w/cord 126-1/2"; cord 10'.
 One medium base lamp, 75w max.



MALBEC NEW

Artisanal glass and high quality craftsmanship offers a signature focal point in the Malbec pendants. Create a customized look suitable for designs from Bohemian to Coastal by grouping several pendants together in a kitchen, entryway or living room setting. Perfectly imperfect, the design offers dimension and visual interest.



P500063-009



FINISHES

- Brushed Nickel - 009
- Antique Bronze - 020
- Graphite - 143

ONE-LIGHT PENDANT

P500063-009 Brushed Nickel with clear glass

P500063-020 Antique Bronze with light blue glass

P500063-143 Graphite with smoked glass

11-3/4" dia., 14" ht.

Overall ht. w/chain 89", wire 10'.

One medium base lamp, 100w max.



ZIN NEW

Inspired by a beautiful wine cask design, the Zin pendants are artfully formed from one large piece of glass. Create a customized look for Rustic Farmhouse and Modern Farmhouse to Urban Industrial settings by grouping several pendants together in a kitchen, entryway or living room setting. Perfectly imperfect, the design offers dimension and visual texture.



P500064-143



FINISHES

- Brushed Nickel - 009
- Antique Bronze - 020
- Graphite - 143

ONE-LIGHT PENDANT

P500064-009 Brushed Nickel with clear glass

P500064-020 Antique Bronze with light blue glass

P500064-143 Graphite with smoked glass

13" dia., 20-3/8" ht.

Overall ht. w/chain 95-1/2", wire 10'

One medium base lamp, 100w max.



CHRONICLE

Chronicle pendants add visual interest and are ideal for commercial-style home kitchens or vintage dining areas. A metal accent ring adds a finishing touch on the glass globe. White opal glass with Polished Nickel finish or clear seeded glass with an Antique Bronze frame are available options.



P5311-20



FINISHES

- Antique Bronze - 20
- Polished Nickel - 104

ONE-LIGHT MINI-PENDANT

P5309-20 Antique Bronze
P5309-104 Polished Nickel
 8" dia., 9" ht.
 Overall ht. w/stem 75"; wire 10'.
 One medium base lamp,
 100w max.

ONE-LIGHT PENDANT

P5311-20 Antique Bronze
P5311-104 Polished Nickel
 12" dia., 13" ht.
 Overall ht. w/stem 79"; wire 10'.
 One medium base lamp,
 100w max.

*Fixtures shown with P7825-01
 vintage lamp*



CAZBAH

One continuous piece of artfully formed glass is suspended by decorative chain-link frame. Cool and modern with a casual flair, Cazbah pendants provide a signature, global look to any room. Minimal frame is finished in either Brushed Nickel or Antique Bronze.



P500031-020



FINISHES

- Brushed Nickel - 009
- Antique Bronze - 020

ONE-LIGHT PENDANT

P500031-009 Brushed Nickel
P500031-020 Antique Bronze
 14-3/8" dia., 28-1/2" ht.
 Overall ht. w/stem 83-1/2"; wire 10'.
 One medium base lamp, 75w max.

*Fixtures shown with P7825-01
 vintage lamp*

ERA

Achieve a vintage feel with Era's carefully crafted details and special eclectic accents. One light pendant or mini pendant options are available in Black with gold leaf accents or Matte White with silver leaf accents.



P500033-031

PENDANTS



N

FINISHES

- White - 030
- Black - 031

MINI-PENDANT

P500032-030 White
P500032-031 Black
 6-3/8" dia., 11-3/4" ht.
 Overall ht. w/cord 78"; cord 10'.
 One medium base lamp,
 60w max.

ONE-LIGHT PENDANT

P500033-030 White
P500033-031 Black
 8-3/8" dia., 16-3/4" ht.
 Overall ht. w/cord 82-1/2"; cord 10'.
 One medium base lamp,
 75w max.

ONE-LIGHT PENDANT

P500098-030 White
P500098-031 Black
 12-3/4" dia., 25" ht.
 Overall ht. w/cord 91", wire 10'.
 One medium base lamp,
 75w max.



N

N New Product

CARBON

Light spills out onto a streamlined shade in the Carbon pendant and mini-pendant. Etched white glass diffuser allows the light to illuminate the Graphite or Polished Nickel shade.



P500014-104



FINISHES

- Polished Nickel - 104
- Graphite - 143

ONE-LIGHT PENDANT

P500013-104 Polished Nickel
P500013-143 Graphite
 11" dia., 8-1/4" ht.
 Overall ht. w/stem 74-1/2"; wire 10'.
 One medium base lamp,
 100w max.

ONE-LIGHT PENDANT

P500014-104 Polished Nickel
P500014-143 Graphite
 19-3/4" dia., 8-1/4" ht.
 Overall ht. w/stem 74-1/2"; wire 10'.
 One medium base lamp,
 100w max.



MESH

Mesh pendants offer an interweaving open cage frame that can serve as a focal point in any lighting design.



P5337-20



FINISH

- Antique Bronze - 20

ONE-LIGHT MINI-PENDANT

P5337-20 Antique Bronze
 8-1/2" dia., 8-3/8" ht.
 Overall ht. w/stem 74-1/2", wire 10'.
 One medium base lamp,
 100w max.

ONE-LIGHT MINI-PENDANT

P5338-20 Antique Bronze
 8-1/2" dia., 8-3/8" ht.
 Overall ht. w/stem 74-1/2", wire 10'.
 One medium base lamp,
 100w max.

*Fixtures shown with P7827-01
 vintage lamp*

FINN

Finn takes a new perspective on an open cage design. The beautifully graphic frame wraps around an etched white glass shade creating a focal aperture for a single lamp. Available in matte Black and Metallic Silver finishes.



P5324-121



FINISHES

- Black - 31
- Metallic Silver - 121

ONE-LIGHT PENDANT

P5324-31 Black
P5324-121 Metallic Silver
 10" dia., 10-1/2" ht.
 Overall ht. w/stem 76-1/2", wire 10'.
 One medium base lamp,
 100w max.

ONE-LIGHT PENDANT

P5325-31 Black
P5325-121 Metallic Silver
 15" dia., 13-1/8" ht.
 Overall ht. w/stem 79", wire 10'.
 One medium base lamp,
 100w max.



MODERNA

Moderna's modern-inspired silhouette provides a signature focal point for a variety of interior spaces. Features clear outer glass with an inner etched white glass shade and a sleek linear frame.



P500000-009-30



P500000-009-30

FINISH

- Brushed Nickel - 009

THREE-LIGHT LED LINEAR CHANDELIER

P400000-009-30 Brushed Nickel
 32" L., 5" W., 16" ht.
 Overall ht. w/stem 82"; wire 15'.
 Three 9w LED modules, 3000K,
 90 CRI, 623 lumens per module.



ONE-LIGHT LED MINI-PENDANT

P500000-009-30 Brushed Nickel
 5-3/4" dia., 9-1/2" ht.
 Overall ht. w/stem 75-1/2"; wire 10'.
 One 9w LED module, 3000K,
 90 CRI, 623 lumens.



P400000-009-30

PARLAY

Parlay helps further nautical-inspired fashion in your decor. The tiered metal shade supports etched glass to offer illumination and task lighting where it's needed. LED source offers energy efficiency, long life and aesthetic benefits to interior spaces.



P5329-2030K9



FINISHES

- Brushed Nickel - 09
- Polished Chrome - 15
- Antique Bronze - 20

LED MINI-PENDANT

P5329-0930K9 Brushed Nickel

P5329-1530K9 Polished Chrome

P5329-2030K9 Antique Bronze

8" dia., 7-5/8" ht.

Overall ht. w/stem 73-1/2"; wire 10'.

One 9w LED module, 3000K,
90 CRI, 623 lumens.



PROGRESS **LED**



CELESTE NEW

Celeste features elegant modern design for an updated traditional appeal. The frame is composed of opposing arched forms to create a beautiful asymmetrical design from any vantage point. Etched opal glass shades add a classic detail to the open frame, while a brilliant Polished Nickel finish completes the design. A perfect choice for Luxe and Mid-Century Modern interiors.



P500124-104



FINISH

- Polished Nickel - 104

MINI-PENDANT

P500123-104 Polished Nickel
 10" sq., 14-3/8" ht.
 Overall ht. w/stem 80-1/2", wire 10'.
 One medium base lamp,
 100w max.

FOUR-LIGHT PENDANT

P500124-104 Polished Nickel
 15-1/8" sq., 23-5/8" ht.
 Overall ht. w/stem 89-1/2", wire 15'.
 Four candelabra base lamps,
 each 60w max.



RE-BAR NEW

Re-Bar pendants are inspired by industrial and vintage electric elements, created from a common masonry structure with a steel reinforcing bar. The coarse material is paired with bright Chrome to provide an intriguing visual contrast. In addition to Urban Industrial and Vintage Electric styles, Re-Bar is ideal for updating Modern Farmhouse interiors.



P5001120-015



FINISH

- Polished Chrome - 015

MINI-PENDANT

P500119-015 Polished Chrome
 12-1/2" Sq., 12-3/8" ht.
 Overall ht. w/stem 78-1/2", wire 10'.
 One medium base lamp,
 60w max.


FOUR-LIGHT PENDANT

P500120-015 Polished Chrome
 21-7/8" Sq., 23" ht.
 Overall ht. w/stem 89", wire 15'.
 Four medium base lamps,
 each 60w max.




FERMI NEW

Cloth cords and sculptural details create an open framework design. Fermi features a geometric frame finished in Brushed Nickel. Red cloth adds a playful contrast to create a unique visual statement. Consider decorative bulbs to further customize Fermi fixtures.



P500045-009

P500044-009



FINISHES


- Brushed Nickel - 009

THREE-LIGHT PENDANT

P500044-009 Brushed Nickel
10" dia., 8" ht.

Overall ht. w/stem 63-1/2", wire 15'.
Three candelabra base lamps,
each 60w max.

P500045-009



FIVE-LIGHT PENDANT

P500045-009 Brushed Nickel
17-3/8" dia., 9" ht.


Overall ht. w/stem 64-1/2", wire 15'.
Five candelabra base lamps,
each 60w max.

SEVEN-LIGHT PENDANT

P500060-009 Brushed Nickel
25-3/8" dia., 13" ht.

Overall ht. w/stem 68-1/2", wire 15'.
Seven candelabra base lamps,
each 60w max.

P500060-009



*Fixtures shown with P7827-01
vintage lamp*

FORMES NEW

The Formes collection features a stately geometric frame to support a single vintage-style lamp. Designed to be used alone or in groupings to create a sophisticated combination. The reflective backplate is an antique mirror that enhances the romantic illumination from this distinctive design.



P710024-020



P710022-020



P710023-020



P710024-020

FINISH

- Antique Bronze - 020

WALL SCONCE

P710022-020 Antique Bronze
7-1/2" W., 14" ht.
Extends 3-3/8". H/CTR 7".
One medium base lamp,
60w max.

WALL SCONCE

P710023-020 Antique Bronze
6-1/2" W., 14" ht.
Extends 3-3/8". H/CTR 7".
One medium base lamp,
60w max.

WALL SCONCE

P710024-020 Antique Bronze
5" W., 14" ht.
Extends 3-3/8". H/CTR 7".
One medium base lamp,
60w max.

*Shown with P7825-01
vintage lamps*

METRO NEW

Metro delivers a clean, geometric form with a pleasing balance of angular metal fittings and a crisp linen shade. The stately fixture adds a modern accent with an elegant sense of architectural distinction.



P710016-015

FINISHES

- Brushed Nickel - 009
- Polished Chrome - 015
- Antique Bronze - 020

WALL BRACKET

P710016-009 Brushed Nickel
P710016-015 Polished Chrome
P710016-020 Antique Bronze
5-1/2" W., 15-1/8" ht.
Extends 7-1/4". H/CTR 10-1/2".
One candelabra base lamp,
60w max.



P710016-015



P710016-009



P710016-020

AVANA NEW

Avana features a graceful tapered candle-arm with a crisp geometric linen shade. The faceted backplate provides a rich architectural detail that complements many fashionable vanity styles.



P710025-009



P710025-009



P710025-020



P710025-104

FINISHES

- Brushed Nickel - 009
- Antique Bronze - 020
- Polished Nickel - 104

WALL BRACKET

P710025-009 Brushed Nickel
P710025-020 Antique Bronze
P710025-104 Polished Nickel
 5-5/8" W., 16" ht.
 Extends 7-1/2". H/CTR 12-1/2".
 One candelabra base lamp,
 60w max.

BONITA NEW

Bonita sconces have a traditional elegance to complement luxurious living with an understated beauty. Crisp metal fittings support a graceful frame and candle topped with a linen shade. Coordinate with Marché or Glimmer collections to add a variation of textures.



P710019-015



FINISHES

- Brushed Nickel - 009
- Polished Chrome - 015
- Antique Bronze - 020

WALL BRACKET

P710018-009 Brushed Nickel
P710018-015 Polished Chrome
P710018-020 Antique Bronze
 9" W., 17-1/8" ht.
 Extends 6-7/8". H/CTR 13-5/8".
 One candelabra base lamp,
 60w max.

WALL BRACKET

P710019-009 Brushed Nickel
P710019-015 Polished Chrome
P710019-020 Antique Bronze
 13-5/8" W., 17-1/8" ht.
 Extends 6-7/8". H/CTR 13-5/8".
 Two candelabra base lamps,
 each 60w max.



HOBBS NEW

Modern traditional design is the combination of crisp geometric forms in classic shapes and materials. Hobbs delivers on this concept with an elegant beveled glass diffuser framing a vintage lamp. The rectangular and circular fittings add a sense of classic craftsmanship for a timeless design.



P710017-015



P710017-009



P710017-015

FINISHES

- Brushed Nickel - 009
- Polished Chrome - 015
- Antique Bronze - 020

WALL SCONCE

P710017-009 Brushed Nickel
P710017-015 Polished Chrome
P710017-020 Antique Bronze
 6" W., 12" ht.
 Extends 4-7/8". H/CTR 6".
 One medium base lamp,
 60w max.

*Shown with P7827-01
 vintage lamps*



P710017-020

VOLO NEW

Volo fixtures feature a modern repeating circular frame. Etched opal glass shades are seamlessly secured to provide a clean, contemporary look to your home. The modern LED source delivers crisp, high quality light that is the perfect choice for both general and task lighting.



P300063-009-30



P300063-009-30



P300063-020-30

FINISHES

- Brushed Nickel - 009
- Antique Bronze - 020

ONE-LIGHT BATH

P300063-009-30 Brushed Nickel
P300063-020-30 Antique Bronze
 10" W., 5-1/2" ht.
 Extends 4-5/8". H/CTR 2-3/4".
 One 9w LED module, 3000K,
 90 CRI, 624 lumens.



TWO-LIGHT BATH

P300064-009-30 Brushed Nickel
P300064-020-30 Antique Bronze
 16" W., 5 1/2" ht.
 Extends 4-5/8". H/CTR 2-3/4".
 Two 9w LED modules, 3000K,
 90 CRI, 624 lumens per module.



THREE-LIGHT BATH

P300065-009-30 Brushed Nickel
P300065-020-30 Antique Bronze
 24" W., 5-1/2" ht.
 Extends 4-5/8". H/CTR 2-3/4".
 Three 9w LED modules, 3000K,
 90 CRI, 624 lumens per module.



*Can be installed vertically
 or horizontally.*



P300064-009-30



P300064-020-30



P300065-009-30



P300065-020-30



ZURA™ NEW

Zura™ features triangular, etched opal glass that provides geometric elements to add modern flair. Available in a Brushed Nickel, Polished Chrome, or Black finish, this contemporary fixture coordinates with the Zura™ Collection by Delta.



P300061-031



P300061-009



P300061-015



P300061-031

FINISHES

- Brushed Nickel - 009
- Polished Chrome - 015
- Black - 031

ONE-LIGHT BATH

P300061-009 Brushed Nickel
P300061-015 Polished Chrome
P300061-031 Black
 4-1/2" W., 13-3/4" ht.
 Extends 7". H/CTR 9-7/8".
 One medium base lamp,
 100w max.

TWO-LIGHT BATH

P300062-009 Brushed Nickel
P300062-015 Polished Chrome
P300062-031 Black
 4-1/2" W., 21" ht.
 Extends 7". H/CTR 10-1/2".
 Two medium base lamps,
 each 100w max.

*Can be installed vertically
 or horizontally.*



P300062-009



P300062-015



P300062-031



P300062-015
shown horizontally



P300062-031
shown horizontally

GLAYSE NEW

Inspired by modern architecture, Glayse features handsome details for variety of interior design styles. The frameless unbounded beveled glass creates beautiful light and reflection. The structure of Glayse is the focal point of the design, where form follows function.



ALSO AVAILABLE IN
Fixture Collections, page 62



P300106-020



P300105-009



P300105-020

FINISHES

- Brushed Nickel - 009
- Antique Bronze - 020

ONE-LIGHT BATH

P300105-009 Brushed Nickel
P300105-020 Antique Bronze
 7" W., 8-3/8" ht.
 Extends 5-1/2". H/CTR 5-3/8".
 One medium base lamp,
 60w max.



P300106-009



P300106-020

TWO-LIGHT BATH

P300106-009 Brushed Nickel
P300106-020 Antique Bronze
 14-7/8" W., 8-3/8" ht.
 Extends 5-1/2". H/CTR 5-3/8".
 Two medium base lamps,
 each 60w max.

THREE-LIGHT BATH

P300107-009 Brushed Nickel
P300107-020 Antique Bronze
 22-3/4" W., 8-3/8" ht.
 Extends 5-1/2". H/CTR 5-3/8".
 Three medium base lamps,
 each 60w max.

*Fixtures shown with P7825-01
 vintage lamps*

Fixture mounts up or down.



P300107-009



P300107-020

UNION SQUARE NEW

Union Square features a reproduction gas lantern inspiration. A Stainless Steel finish complements the natural polished material and clear flat glass panels. Mechanical details – such as exaggerated knobs – provide character to the form. Open top and bottom on fixture provides easy access for cleaning and relamping.



ALSO AVAILABLE IN

Outdoor, page 248



P300135-135

*shown with P7825-01
vintage lamps*



P710038-135

*shown with P7825-01
vintage lamp*



P710038-135

*shown with P7827-01
vintage lamp*



P300135-135

*shown with P7825-01
vintage lamps*



P300135-135

*shown with P7827-01
vintage lamps*



P300135-135

*shown with P7825-01
vintage lamps*



P300136-135

*shown with P7825-01
vintage lamps*



P300136-135

*shown with P7827-01
vintage lamps*

FINISH

- Stainless Steel - 135

TWO-LIGHT BATH

P300135-135 Stainless Steel
16" W., 4-1/2" ht.
Extends 5". H/CTR 2-1/4".
Two medium base lamps,
each 60w max.

FOUR-LIGHT BATH

P300136-135 Stainless Steel
30" W., 4-1/2" ht.
Extends 5". H/CTR 2-1/4".
Four medium base lamps,
each 60w max.

ONE-LIGHT BRACKET

P710038-135 Stainless Steel
5-1/4" sq., 12" ht.
Extends 5". H/CTR 6".
One medium base lamp,
60w max.

*Can be installed vertically or
horizontally.*




P300136-135

*shown with P7827-01
vintage lamps*

SPATIAL NEW

Spatial showcases a modern form that complements Urban Industrial, Mid-Century and Bohemian styles. Overscale geometric frames feature designs inspired by metal trusses and the art of engineering. A Matte Black finish is highlighted by clear globe shades or open candles. Chandelier and pendant options are ideal for foyers and entryways, while vanity fixtures complement modern spa-like bath suites.



ALSO AVAILABLE IN
Fixture Collections, page 72



P300113-031



P300112-031



P300113-031



P300114-031



P300115-031

FINISH

- Black - 031

ONE-LIGHT BATH

P300112-031 Black
5-3/8" W., 6-1/2" ht.
Extends 8". H/CTR 3-3/8".
One G16.5 candelabra base lamp,
60w max.

TWO-LIGHT BATH

P300113-031 Black
14-1/8" W., 6-1/2" ht.
Extends 8-1/2". H/CTR 2-5/8".
Two G16.5 candelabra base lamps,
each 60w max.

THREE-LIGHT BATH

P300114-031 Black
22" W., 6-1/2" ht.
Extends 8-1/2". H/CTR 2-5/8".
Three G16.5 candelabra base lamps,
each 60w max.

FOUR-LIGHT BATH

P300115-031 Black
31-1/8" W., 6-1/2" ht.
Extends 8-1/2". H/CTR 2-5/8".
Four G16.5 candelabra base lamps,
each 60w max.

Fixture mounts up or down.

MOD

Giving a nod to the space age with mid-century modern appeal. Mod features a sleek linear frame in a Polished Chrome finish. Clear, spherical glass shades offer the perfect focal point for vintage bulbs or reflector-style globes.



ALSO AVAILABLE IN
Fixture Collections, page 78



P2854-15



P2850-15



P2854-15



P2856-15



P2857-15

FINISH

- Polished Chrome - 15

ONE-LIGHT BATH

P2850-15 Polished Chrome
5-7/8" W., 7-3/4" ht.
Extends 7-3/8". H/CTR 3-7/8".
One candelabra base lamp,
60w max.

TWO-LIGHT BATH

P2854-15 Polished Chrome
15" W., 6-3/4" ht.
Extends 7-3/8". H/CTR 2-3/8".
Two candelabra base lamps,
each 60w max.

THREE-LIGHT BATH

P2856-15 Polished Chrome
24" W., 6-3/4" ht.
Extends 7-3/8". H/CTR 2-3/8".
Three candelabra base lamps,
each 60w max.

FOUR-LIGHT BATH

P2857-15 Polished Chrome
33" W., 6-3/4" ht.
Extends 7-3/8". H/CTR 2-3/8".
Four candelabra base lamps,
each 60w max.

*Fixtures shown with P7826-01
vintage lamps*

Fixture mounts up or down.

SOIREE

Featuring a handsome, repeating geometric pattern and an updated iron frame, Soiree offers a touch of sparkle to any room. Tall candles are highlighted by a hand painted Champagne finish. The glass shades in the bath, mini pendant and chandelier fixtures are secured with a locking ring – offering form and function for each fixture within the collection.



ALSO AVAILABLE IN
Fixture Collections, page 106



P300037-020



P300035-020



P300036-020



P300037-020



P300038-020

FINISH

- Antique Bronze - 020

ONE-LIGHT BATH

P300035-020 Antique Bronze
4-3/4" W., 21" ht.
Extends 6". H/CTR 8-5/8".
One candelabra base lamp,
60w max.

TWO-LIGHT BATH

P300036-020 Antique Bronze
14-1/8" W., 11-1/2" ht.
Extends 6". H/CTR 7".
Two candelabra base lamps,
each 60w max.

THREE-LIGHT BATH

P300037-020 Antique Bronze
23-3/4" W., 11-1/2" ht.
Extends 6". H/CTR 7".
Three candelabra base lamps,
each 60w max.

FOUR-LIGHT BATH

P300038-020 Antique Bronze
33-1/2" W., 11-1/2" ht.
Extends 6". H/CTR 7".
Four candelabra base lamps,
each 60w max.


*Fixtures shown with P7826-01
vintage lamps*

Fixture mounts up or down.

CAHILL

NEW

A stylish Brushed Bronze finish frames brilliant clear beveled glass panels in the Cahill collection. Ideal for Luxe or Mid-Century Modern interiors, the visual interest provides a reinvention of the popular glass design.



ALSO AVAILABLE IN
Fixture Collections, page 46



P300109-109



P300108-109



P300109-109



P300110-109



P300111-109

FINISH

- Brushed Bronze - 109

ONE-LIGHT BATH

P300108-109 Brushed Bronze
4-1/2" W., 19-3/4" ht.
Extends 7-1/2".
One candelabra base lamp,
60w max.

TWO-LIGHT BATH

P300109-109 Brushed Bronze
16-3/4" W., 6-3/8" ht.
Extends 5-1/4". H/CTR 3-1/8".
Two candelabra base lamps,
each 60w max.

THREE-LIGHT BATH

P300110-109 Brushed Bronze
24" W., 6-3/8" ht.
Extends 5-1/4". H/CTR 3-1/8".
Three candelabra base lamps,
each 60w max.

FOUR-LIGHT BATH

P300111-109 Brushed Bronze
30" W., 6-3/8" ht.
Extends 5-1/4". H/CTR 3-1/8".
Four candelabra base lamps,
each 60w max.

*Fixtures shown with P7826-01
vintage lamps*

Fixture mounts up or down.

ELEVATE

Achieve a mid-century modern look with Elevate, which boasts glass shades and a frame inspired by modern styling. Brushed Bronze and Polished Chrome finish options available.



ALSO AVAILABLE IN
Fixture Collections, page 74



P300021-109



P300020-109



P300022-109



P300023-109



P300020-015



P300021-015



P300022-015



P300023-015

FINISHES

- Polished Chrome - 015
- Brushed Bronze - 109

ONE-LIGHT BATH

P300020-015 Polished Chrome
P300020-109 Brushed Bronze
 5" W., 8" ht.
 Extends 7". H/CTR 4".
 One medium base lamp,
 100w max.

TWO-LIGHT BATH

P300021-015 Polished Chrome
P300021-109 Brushed Bronze
 15-3/8" W., 7-1/2" ht.
 Extends 6-1/8". H/CTR 5".
 Two medium base lamps,
 each 100w max.

THREE-LIGHT BATH

P300022-015 Polished Chrome
P300022-109 Brushed Bronze
 24-3/4" W., 7-1/2" ht.
 Extends 8". H/CTR 5".
 Three medium base lamps,
 each 100w max.

FOUR-LIGHT BATH

P300023-015 Polished Chrome
P300023-109 Brushed Bronze
 34-1/2" W., 7-1/2" ht.
 Extends 7-3/4". H/CTR 5".
 Four medium base lamps,
 each 100w max.

Fixture mounts up or down.

DEBUT

Delicate details and warm finish options, including Graphite and Brushed Nickel, create statement making focal pieces for a variety of interiors. Debut provides a fitting stage to feature nostalgic, vintage lamps. Glass accessory shades in clear or frosted seeded finishes are available to complement traditional incandescent or energy efficient lamps.



ALSO AVAILABLE IN
Fixture Collections, page 90



P300009-143
*Shown with seeded glass
shade P860003-001*



P300008-143



P300010-143
Shown with seeded glass shade P860003-001



P300011-143
Shown with etched glass shade P860002-001



P300008-009
Shown with seeded glass shade P860003-001



P300009-009
Shown with etched glass shade P860002-001



P300010-009
Shown with seeded glass shade P860003-001



P300011-009

FINISHES

- Brushed Nickel - 009
- Graphite - 143

ONE-LIGHT BATH

P300008-009 Brushed Nickel
P300008-143 Graphite
4-1/2" W., 8-1/2" ht.
Extends 5-7/8". H/CTR 5".
One medium base lamp, 60w max.

TWO-LIGHT BATH

P300009-009 Brushed Nickel
P300009-143 Graphite
14-1/4" W., 7-7/8" ht.
Extends 5-3/4". H/CTR 5-5/8".
Two medium base lamps, each 60w max.

THREE-LIGHT BATH

P300010-009 Brushed Nickel
P300010-143 Graphite
23-3/4" W., 7-7/8" ht.
Extends 8". H/CTR 5-5/8".
Three medium base lamps, each 60w max.

FOUR-LIGHT BATH

P300011-009 Brushed Nickel
P300011-143 Graphite
30-1/4" W., 7-7/8" ht.
Extends 8". H/CTR 5-5/8".
Four medium base lamps, each 60w max.

P860002-001
Etched glass shade.

P860003-001
Seeded glass shade.

Fixtures shown with P7825-01 vintage lamps

Fixture mounts up or down.




P860002-001



P860003-001

LOGIC

The Logic collection is defined by a sleek, modern design. Tapered etched glass shades and a full back plate complete the one- through four-light bath and vanity fixtures. Polished Chrome and Brushed Nickel finish options available.



P2155-09



P2154-09



P2155-09



P2156-09



P2157-09



P2154-15



P2155-15



P2156-15



P2157-15

FINISHES

- Brushed Nickel - 09
- Polished Chrome - 15

ONE-LIGHT BATH

P2154-09 Brushed Nickel

P2154-15 Polished Chrome

4-1/2" W., 8-1/4" ht.

Extends 5-3/4". H/CTR 5-7/8".

One medium base lamp,
100w max.

TWO-LIGHT BATH

P2155-09 Brushed Nickel

P2155-15 Polished Chrome

12-1/2" W., 8-1/4" ht.

Extends 5-3/4". H/CTR 5-7/8".

Two medium base lamps,
each 100w max.

THREE-LIGHT BATH

P2156-09 Brushed Nickel

P2156-15 Polished Chrome

24" W., 8-1/4" ht.

Extends 5-3/4". H/CTR 5-7/8".

Three medium base lamps,
each 100w max.

FOUR-LIGHT BATH

P2157-09 Brushed Nickel

P2157-15 Polished Chrome

30" W., 8-1/4" ht.

Extends 5-3/4". H/CTR 5-7/8".

Four medium base lamps,
each 100w max.

Fixture mounts up or down.

FLIGHT

The Flight bath and vanity collection features a variety of industrial modern elements, including a linear frame and circular wall plate. The geometric and linear design is complemented by Brushed Nickel and Polished Chrome finish options.



P300001-009



P300000-009



P300001-009



P300002-009



P300003-009



P300000-015



P300001-015



P300002-015



P300003-015

FINISHES

- Brushed Nickel - 009
- Polished Chrome - 015

ONE-LIGHT BATH

P300000-009 Brushed Nickel
P300000-015 Polished Chrome
 6-1/8" W., 8-1/4" ht.
 Extends 5-5/8". H/CTR 5-1/8".
 One medium base lamp,
 100w max.

TWO-LIGHT BATH

P300001-009 Brushed Nickel
P300001-015 Polished Chrome
 15-3/4" W., 8-1/4" ht.
 Extends 5-5/8". H/CTR 5-1/8".
 Two medium base lamps,
 each 100w max.

THREE-LIGHT BATH

P300002-009 Brushed Nickel
P300002-015 Polished Chrome
 26-1/4" W., 8-1/4" ht.
 Extends 5-5/8". H/CTR 5-1/8".
 Three medium base lamps,
 each 100w max.

FOUR-LIGHT BATH

P300003-009 Brushed Nickel
P300003-015 Polished Chrome
 36-3/4" W., 8-1/4" ht.
 Extends 5-5/8". H/CTR 5-1/8".
 Four medium base lamps,
 each 100w max.

Fixture mounts up or down.

WEST VILLAGE

Visual interest continues with a three-spoke design that holds each glass shade. Brushed Nickel with chrome accents or Antique Bronze with antique brass accents provide touches of mixed metal in all fixtures within the collection.



ALSO AVAILABLE IN
Fixture Collections, page 116



P300005-020



P300004-009



P300005-009



P300006-009



P300007-009



P300004-020



P300005-020



P300006-020



P300007-020

FINISHES

- Brushed Nickel - 009
- Antique Bronze - 020

ONE-LIGHT BATH

P300004-009 Brushed Nickel
P300004-020 Antique Bronze
 5-1/8" W., 8-1/8" ht.
 Extends 7". H/CTR 4-1/8".
 One medium base lamp,
 100w max.

TWO-LIGHT BATH

P300005-009 Brushed Nickel
P300005-020 Antique Bronze
 14-1/8" W., 8-1/8" ht.
 Extends 7". H/CTR 6".
 Two medium base lamps,
 each 100w max.

THREE-LIGHT BATH

P300006-009 Brushed Nickel
P300006-020 Antique Bronze
 23-1/4" W., 8-1/8" ht.
 Extends 7". H/CTR 6".
 Three medium base lamps,
 each 100w max.

FOUR-LIGHT BATH

P300007-009 Brushed Nickel
P300007-020 Antique Bronze
 32-1/4" W., 8-1/8" ht.
 Extends 7". H/CTR 6".
 Four medium base lamps,
 each 100w max.

Fixture mounts up or down.

CARLYN NEW

With a glamorous, transitional appeal, Carlyn bath and vanity fixtures feature a luxurious pattern comprised of K9 glass accents. The inner lined glass shades glimmer against both finishes.



P300101-104



FINISHES

- Antique Bronze - 020
- Polished Nickel - 104

ONE-LIGHT BATH

P300100-020 Antique Bronze
P300100-104 Polished Nickel
 5-1/8" W., 11-7/8" ht.
 Extends 5-7/8". H/CTR 6-5/8".
 One medium base lamp,
 100w max.

TWO-LIGHT BATH

P300101-020 Antique Bronze
P300101-104 Polished Nickel
 13-1/2" W., 8" ht.
 Extends 6-3/8". H/CTR 5-3/4".
 Two medium base lamps,
 each 100w max.

THREE-LIGHT BATH

P300102-020 Antique Bronze
P300102-104 Polished Nickel
 22-5/8" W., 8" ht.
 Extends 6-3/8". H/CTR 5-3/4".
 Three medium base lamps,
 each 100w max.

FOUR-LIGHT BATH

P300103-020 Antique Bronze
P300103-104 Polished Nickel
 31-7/8" W., 8" ht.
 Extends 6-3/8". H/CTR 5-3/4".
 Four medium base lamps,
 each 100w max.

Fixture mounts up or down.

GLANCE

A sophisticated bath and vanity collection. Glance's stout frame and etched linen glass shades complement a variety of contemporary design schemes. Polished Chrome and Antique Bronze finishes available for the one- through four-light fixtures.



P300017-015



P300016-015



P300017-015



P300018-015



P300019-015



P300016-020



P300017-020



P300018-020



P300019-020

FINISHES

- Polished Chrome - 015
- Antique Bronze - 020

ONE-LIGHT BATH

P300016-015 Polished Chrome
P300016-020 Antique Bronze
 5-3/8" W., 7-1/4" ht.
 Extends 7-1/4". H/CTR 3-5/8".
 One medium base lamp,
 100w max.

TWO-LIGHT BATH

P300017-015 Polished Chrome
P300017-020 Antique Bronze
 14-1/2" W., 7-1/4" ht.
 Extends 7-1/4". H/CTR 3-5/8".
 Two medium base lamps,
 each 100w max.

THREE-LIGHT BATH

P300018-015 Polished Chrome
P300018-020 Antique Bronze
 24" W., 7-1/4" ht.
 Extends 7-1/4". H/CTR 3-5/8".
 Three medium base lamps,
 each 100w max.

FOUR-LIGHT BATH

P300019-015 Polished Chrome
P300019-020 Antique Bronze
 33-3/8" W., 7-1/4" ht.
 Extends 7-1/4". H/CTR 3-5/8".
 Four medium base lamps,
 each 100w max.

Fixture mounts up or down.

GLIDE

Let Glide's nautical-inspired bath and vanity collection bring elegance and a spa-like atmosphere into the home. Available in Brushed Nickel, Polished Chrome or Rubbed Bronze, the oval-shaped opal glass sits upon a pedestal while offering a traditional or formal style. One-through four-light vanity options.



P300013-009



P300012-009



P300013-009



P300012-009
mounted down



P300013-009
mounted down



P300014-009



P300015-009

FINISH

- Brushed Nickel - 009

ONE-LIGHT BATH

P300012-009 Brushed Nickel
4-1/2" W., 8" ht.
Extends 6". H/CTR 4".
One medium base lamp,
100w max.

TWO-LIGHT BATH

P300013-009 Brushed Nickel
16" W., 7-3/4" ht.
Extends 6-7/8". H/CTR 4".
Two medium base lamps,
each 100w max.

THREE-LIGHT BATH

P300014-009 Brushed Nickel
24" W., 7-3/4" ht.
Extends 6-7/8". H/CTR 4".
Three medium base lamps,
each 100w max.

FOUR-LIGHT BATH

P300015-009 Brushed Nickel
34" W., 7-3/4" ht.
Extends 6-3/4". H/CTR 4".
Four medium base lamps,
each 100w max.

Fixture mounts up or down.

GLIDE

FINISHES

- Polished Chrome - 015

ONE-LIGHT BATH

P300012-015 Polished Chrome
4-1/2" W., 8" ht.
Extends 6". H/CTR 4".
One medium base lamp,
100w max.



P300012-015



P300013-015

TWO-LIGHT BATH

P300013-015 Polished Chrome
16" W., 7-3/4" ht.
Extends 6-7/8". H/CTR 4".
Two medium base lamps,
each 100w max.



P300012-015
mounted down



P300013-015
mounted down

THREE-LIGHT BATH

P300014-015 Polished Chrome
24" W., 7-3/4" ht.
Extends 6-7/8". H/CTR 4".
Three medium base lamps,
each 100w max.



P300014-015

FOUR-LIGHT BATH

P300015-015 Polished Chrome
34" W., 7-3/4" ht.
Extends 6-3/4". H/CTR 4".
Four medium base lamps,
each 100w max.



P300015-015

Fixture mounts up or down.

GLIDE

FINISHES

- Rubbed Bronze - 139

ONE-LIGHT BATH

P300012-139 Rubbed Bronze
4-1/2" W., 8" ht.
Extends 6". H/CTR 4".
One medium base lamp,
100w max.



P300012-139



P300013-139

TWO-LIGHT BATH

P300013-139 Rubbed Bronze
16" W., 7-3/4" ht.
Extends 6-7/8". H/CTR 4".
Two medium base lamps,
each 100w max.



P300012-139
mounted down



P300013-139
mounted down

THREE-LIGHT BATH

P300014-139 Rubbed Bronze
24" W., 7-3/4" ht.
Extends 6-7/8". H/CTR 4".
Three medium base lamps,
each 100w max.



P300014-139

FOUR-LIGHT BATH

P300015-139 Rubbed Bronze
34" W., 7-3/4" ht.
Extends 6-3/4". H/CTR 4".
Four medium base lamps,
each 100w max.



P300015-139

Fixture mounts up or down.

WANDER

A Victorian-inspired bath and vanity collection, Wander wall brackets offer a clean and classic look. Etched glass shades are paired with a Polished Chrome, Brushed Nickel or Venetian Bronze finish to offer versatile styling for any home.



P300025-009



P300024-009



P300025-009



P300024-009
mounted up



P300025-009
mounted up



P300026-009



P300027-009

FINISH

- Brushed Nickel - 009

ONE-LIGHT BATH

P300024-009 Brushed Nickel
4-3/4" W., 8-7/8" ht.
Extends 7". H/CTR 5-3/8".
One medium base lamp,
100w max.

TWO-LIGHT BATH

P300025-009 Brushed Nickel
16" W., 8-1/4" ht.
Extends 7". H/CTR 5".
Two medium base lamps,
each 100w max.

THREE-LIGHT BATH

P300026-009 Brushed Nickel
24-1/2" W., 8-1/4" ht.
Extends 7". H/CTR 5".
Three medium base lamps,
each 100w max.

FOUR-LIGHT BATH

P300027-009 Brushed Nickel
34" W., 8-1/4" ht.
Extends 7". H/CTR 5".
Four medium base lamps,
each 100w max.

Fixture mounts up or down.

WANDER

FINISHES

- Polished Chrome - 015

ONE-LIGHT BATH

P300024-015 Polished Chrome
4-3/4" W., 8-7/8" ht.
Extends 7". H/CTR 5-3/8".
One medium base lamp,
100w max.



P300024-015



P300025-015

TWO-LIGHT BATH

P300025-015 Polished Chrome
16" W., 8-1/4" ht.
Extends 7". H/CTR 5".
Two medium base lamps,
each 100w max.



P300024-015
mounted up



P300025-015
mounted up

THREE-LIGHT BATH

P300026-015 Polished Chrome
24-1/2" W., 8-1/4" ht.
Extends 7". H/CTR 5".
Three medium base lamps,
each 100w max.



P300026-015

FOUR-LIGHT BATH

P300027-015 Polished Chrome
34" W., 8-1/4" ht.
Extends 7". H/CTR 5".
Four medium base lamps,
each 100w max.



P300027-015

Fixture mounts up or down.

WANDER

FINISHES

- Venetian Bronze - 074

ONE-LIGHT BATH

P300025-074 Venetian Bronze
4-3/4" W., 8-7/8" ht.
Extends 7". H/CTR 5-3/8".
One medium base lamp,
100w max.

TWO-LIGHT BATH

P300025-074 Venetian Bronze
16" W., 8-1/4" ht.
Extends 7". H/CTR 5".
Two medium base lamps,
each 100w max.

THREE-LIGHT BATH

P300026-074 Venetian Bronze
24-1/2" W., 8-1/4" ht.
Extends 7". H/CTR 5".
Three medium base lamps,
each 100w max.

FOUR-LIGHT BATH

P300027-074 Venetian Bronze
34" W., 8-1/4" ht.
Extends 7". H/CTR 5".
Four medium base lamps,
each 100w max.

Fixture mounts up or down.



P300024-074



P300025-074



P300024-074
mounted up



P300025-074
mounted up



P300026-074



P300027-074

METRIC

A simple, etched opal glass shade nestles inside a die-cast frame that is finished in either Polished Chrome or Brushed Nickel – providing light above and below the fixture.



ALSO AVAILABLE IN

Fixture Collections, page 120



P2194-09



P2193-09



P2193-15



P2194-09



P2194-15




P2195-09



P2195-15



P2196-09



P2196-15

FINISH

- Brushed Nickel - 09
- Polished Chrome - 15

ONE-LIGHT BATH

P2193-09 Brushed Nickel

P2193-15 Polished Chrome

4-5/8" W., 8" ht.

Extends 5-1/4". H/CTR 4-1/8".

One medium base lamp, 100w max.

TWO-LIGHT BATH

P2194-09 Brushed Nickel

P2194-15 Polished Chrome

13" W., 6-1/2" ht.

Extends 5-1/4". H/CTR 4-1/8".

Two medium base lamps each, 100w max.

THREE-LIGHT BATH

P2195-09 Brushed Nickel

P2195-15 Polished Chrome

22-1/8" W., 6-1/2" ht.

Extends 5-1/4". H/CTR 4-1/8".

Three medium base lamps each, 100w max.

FOUR-LIGHT BATH

P2196-09 Brushed Nickel

P2196-15 Polished Chrome

31-1/4" W., 6-1/2" ht.

Extends 5-1/4". H/CTR 4-1/8".

Four medium base lamps each, 100w max.

Fixture mounts up or down.

CADENCE GU24

Clear seeded water glass panes with etched pillar diffuser uses energy efficient compact fluorescent lamps.



P6539-31



P6626-31



P6628-31



P6629-31



P6539-31



P6627-31



P6439-31

FINISH

- Black - 31

POST LANTERN

P6439-31 Black
10" dia., 23" ht.
Fits 3" post (order separately).
One GU24 base lamp,
26w max.



HANGING LANTERN

P6539-31 Black
10" dia., 24-5/8" ht.
Overall ht. w/chain 100", wire 10'.
One GU24 base lamp,
26w max.



SMALL WALL LANTERN

P6626-31 Black
6-1/8" W., 18-7/8" ht.
Extends 7-1/2". H/CTR 9-1/4".
One GU24 base lamp,
18w max.



MEDIUM WALL LANTERN

P6627-31 Black
8" W., 24-3/4" ht.
Extends 9-1/4". H/CTR 13-3/8".
One GU24 base lamp,
26w max.



LARGE WALL LANTERN

P6628-31 Black
10" W., 31" ht.
Extends 11-3/8". H/CTR 14-1/8".
One GU24 base lamp,
26w max.



*EXTRA-LARGE
WALL LANTERN*

P6629-31 Black
12" W., 38" ht.
Extends 13-1/4". H/CTR 18-1/4".
One GU24 base lamp,
26w max.



CADENCE

The Cadence lantern collection showcases classic styling. Clear water glass panels showcase traditional lighting clusters. Mediterranean-style frame is finished in Oil Rubbed Bronze.



P6542-108



P6080-108



P6542-108



P6639-108



P6638-108



P6640-108



P6442-108

FINISH

- Oil Rubbed Bronze - 108

SMALL WALL-LANTERN

P6080-108 Oil Rubbed Bronze
6" W., 16-1/4" ht.
Extends 7-1/4". H/CTR 7-3/4".
One medium base lamp,
100w max.

POST LANTERN

P6442-108 Oil Rubbed Bronze
10" sq., 22-5/8" ht.
Fits 3" post (order separately).
Three candelabra base lamps,
each 60w max.

HANGING LANTERN

P6542-108 Oil Rubbed Bronze
10" sq., 24" ht.
Overall ht. w/chain 99-1/2"; wire 15'.
Three candelabra base lamps,
each 60w max.

MEDIUM WALL LANTERN

P6638-108 Oil Rubbed Bronze
8" W., 21-1/4" ht.
Extends 9-3/8". H/CTR 9-7/8".
Two candelabra base lamps,
each 60w max.

LARGE WALL LANTERN

P6639-108 Oil Rubbed Bronze
10" W., 26-5/8" ht.
Extends 11-1/2". H/CTR 9-5/8".
Three candelabra base lamps,
each 60w max.

*EXTRA-LARGE
WALL LANTERN*

P6640-108 Oil Rubbed Bronze
12-1/4" W., 32" ht.
Extends 13-3/4". H/CTR 11-5/8".
Four candelabra base lamps,
each 60w max.

MAISON GU24

Maison offers French country styling for a variety of home settings. Classic and formal clear water seeded glass in a die-cast aluminum frame. GU24 version with etched pillar diffuser.



P6541-31



P6634-31



P6541-31



P6636-31



P6635-31



P6637-31



P6441-31

FINISH

- Black - 31

POST LANTERN

P6441-31 Black
10-1/2" dia., 26-3/8" ht.
Fits 3" post (order separately).
One GU24 base lamp,
26w max.



HANGING LANTERN

P6541-31 Black
10-1/2" dia., 24-1/2" ht. Overall ht.
w/chain 100-1/2", wire 10'.
One GU24 base lamp,
26w max.



SMALL WALL LANTERN

P6634-31 Black
5-3/4" W., 13-5/8" ht.
Extends 6-1/8". H/CTR 9-1/8".
One GU24 base lamp,
18w max.



MEDIUM WALL LANTERN

P6635-31 Black
7-1/4" W., 16-7/8" ht.
Extends 7-7/8". H/CTR 11-3/4".
One GU24 base lamp,
26w max.



LARGE WALL LANTERN

P6636-31 Black
8-1/2" W., 19-3/4" ht.
Extends 8-7/8". H/CTR 13-3/8".
One GU24 base lamp,
26w max.



*EXTRA-LARGE
WALL LANTERN*

P6637-31 Black
10-1/2" W., 23-3/4" ht.
Extends 11-1/4". H/CTR 16-3/8".
One GU24 base lamp,
26w max.



WHITACRE NEW

Inspired by traditional lantern styles, Whitacre incorporates handsome details. Clear seeded glass surrounds an etched opal glass candle diffuser. An Antique Bronze finish complements a variety of exteriors, including Transitional and Traditional and Farmhouse designs.



P550026-020-30



P560068-020-30



P560069-020-30



P560070-020-30



P550026-020-30



P540026-020-30

FINISH

- Antique Bronze - 020

POST LANTERN

P540026-020-30 Antique Bronze
12-5/16" dia., 22-7/8" ht.
Fits 3" post (order separately).
One 9w LED module, 3000K, 90 CRI, 624 lumens.



HANGING LANTERN

P550026-020-30 Antique Bronze
12-5/16" dia., 21" ht.
Overall ht. w/chain 96", wire 10'.
One 17w LED module, 3000K, 90 CRI, 1276 lumens.



SMALL WALL LANTERN

P560068-020-30 Antique Bronze
7-7/8" W., 14-3/8" ht.
Extends 8". H/CTR 3-5/8".
One 9w LED module, 3000K, 90 CRI, 624 lumens.



MEDIUM WALL LANTERN

P560069-020-30 Antique Bronze
10" W., 18" ht.
Extends 10". H/CTR 4".
One 9w LED module, 3000K, 90 CRI, 624 lumens.



LARGE WALL LANTERN

P560070-020-30 Antique Bronze
12-5/16" W., 22" ht.
Extends 12". H/CTR 4-3/4".
One 17w LED module, 3000K, 90 CRI, 1276 lumens.



HERMOSA NEW

Outdoor Mediterranean-style lanterns in the Hermosa family complement Transitional, Rustic Farmhouse and Modern Farmhouse exteriors. These large-scale pieces feature beautiful detail and a die cast aluminum frames. Wrought iron styling perfectly frames beautiful clear, water glass shades.



P550027-031



P560074-031



P560075-031



P560076-031



P550027-031



P540027-031

FINISH

- Black - 031

POST LANTERN

P540027-031 Black
12" dia., 28" ht.
Fits 3" post (order separately).
One medium base lamp,
100w max.

HANGING LANTERN

P550027-031 Black
12" dia., 26-1/2" ht.
Overall ht. w/chain 101-1/2", wire 10'.
One medium base lamp,
100w max.

SMALL WALL LANTERN

P560074-031 Black
8" W., 21" ht.
Extends 8-1/4". H/CTR 12-7/8".
One medium base lamp,
100w max.

MEDIUM WALL LANTERN


P560075-031 Black
10" W., 26" ht.
Extends 10-1/8". H/CTR 16-1/8".
One medium base lamp,
100w max.

LARGE WALL LANTERN

P560076-031 Black
12" W., 32" ht.
Extends 12-1/4". H/CTR 20-1/8".
One medium base lamp,
100w max.

CRAWFORD GU24

Transform the outdoors with timeless styling.
Die-cast aluminum with clear water seeded
glass. Energy efficient. Powder coat finish.
Hinged door for easy relamping.*



P6540-31



P6631-31



P6632-31



P6633-31



P6540-31



P6630-31



P6440-31

FINISH

- Black - 31

POST LANTERN

P6440-31 Black
 9-7/8" W., 24-5/8" ht.
 Fits 3" post (order separately).
 One GU24 base lamp,
 26w max.



*HANGING LANTERN**

P6540-31 Black
 9-7/8" dia., 26-5/8" ht.
 Overall ht. w/ chain 102"; wire 10'.
 One GU24 base lamp,
 26w max.



*SMALL WALL LANTERN**

P6630-31 Black
 6-1/2" W., 1-1/2" ht.
 Extends 8-3/4". H/CTR 8".
 One GU24 base lamp,
 26w max.



*MEDIUM WALL LANTERN**

P6631-31 Black
 8-1/2" W., 20-1/2" ht.
 Extends 11".
 H/CTR 8-3/8".
 One GU24 base lamp,
 26w max.



*LARGE WALL LANTERN**

P6632-31 Black
 9-7/8" W., 28-7/8" ht.
 Extends 12-5/8". H/CTR 8-3/8".
 One GU24 base lamp,
 26w max.




*EXTRA-LARGE
 WALL LANTERN*

P6633-31 Black
 12" W., 32-7/8" ht.
 Extends 14-3/4". H/CTR 14-7/8".
 One GU24 base lamp,
 26w max.



ANDOVER GU24

Clear seeded water glass panes with etched pillar diffuser. GU24 sockets for use with energy efficient lamps.



P6538-31



P6619-31



P6621-31



P6622-31



P6538-31



P6620-31



P6438-31

FINISH

- Black - 31

POST LANTERN

P6438-31 Black
 9-1/2" dia., 22-3/8" ht.
 Fits 3" post (order separately).
 One GU24 base lamp,
 26w max.



HANGING LANTERN

P6538-31 Black
 12-1/2" dia., 25-1/4" ht.
 Overall ht. w/chain 100-1/2", wire 10'.
 One GU24 base lamp,
 26w max.



SMALL WALL LANTERN

P6619-31 Black
 5-5/8" W., 13-3/8" ht.
 Extends 6-3/4". H/CTR 6-3/8".
 One GU24 base lamp,
 18w max.



MEDIUM WALL LANTERN

P6620-31 Black
 7-1/2" W., 18-3/8" ht.
 Extends 8-3/8". H/CTR 10-1/2".
 One GU24 base lamp,
 26w max.



LARGE WALL LANTERN

P6621-31 Black
 9-1/2" W., 26-1/4" ht.
 Extends 10-1/4". H/CTR 12-3/4".
 One GU24 base lamp,
 26w max.



EXTRA-LARGE WALL LANTERN

P6622-31 Black
 12-1/2" W., 34-3/8" ht.
 Extends 13-1/2". H/CTR 18-5/8".
 One GU24 base lamp,
 26w max.



DEVEREUX

Devereux features an etched white pillar shade that sits inside a clear seeded glass design. A double scrolled arm finished in Antique Bronze provides elegant scale for a variety of exterior settings. Post, hanging and wall lantern options are available.



P550003-020



P560018-020



P560019-020



P560020-020



P550003-020



P540003-020

FINISH

- Antique Bronze - 020

POST LANTERN

P540003-020 Antique Bronze
9-3/8" dia., 26-5/8" ht.
Fits 3" post (order separately).
One medium base lamp,
100w max.

HANGING LANTERN

P550003-020 Antique Bronze
9-1/2" dia., 23-5/8" ht.
Overall ht. w/chain 95-1/2"; wire 10'.
One medium base lamp,
100w max.

SMALL WALL-LANTERN

P560018-020 Antique Bronze
5-1/2" W., 20-1/4" ht.
Extends 7-7/8". H/CTR 10-1/8".
One medium base lamp,
100w max.

MEDIUM WALL-LANTERN

P560019-020 Antique Bronze
7" W., 26" ht.
Extends 9-3/4". H/CTR 13".
One medium base lamp,
100w max.

LARGE WALL-LANTERN

P560020-020 Antique Bronze
9-1/2" W., 34-1/2" ht.
Extends 12-3/4". H/CTR 17-3/8".
One medium base lamp,
100w max.

VERDAE

Classic and formal clear seeded glass complements a Black or Antique Bronze finish. Open bottom or hinged door provide easy access for cleaning and relamping.



P560016-020



P560014-020



P560014-031



P550002-020



P560015-020



P560015-031



P550002-031



P560016-020



P560016-031



FINISHES

- Antique Bronze - 020
- Black - 031

POST LANTERN

P540002-020 Antique Bronze
P540002-031 Black
 10-3/8" dia., 22-5/8" ht.
 Fits 3" post (order separately).
 Three candelabra base lamps,
 each 60w max.

HANGING LANTERN

P550002-020 Antique Bronze
P550002-031 Black
 10-3/8" dia., 18-3/8" ht.
 Overall ht. w/chain 93-1/2"; wire 10'.
 Three candelabra base lamps,
 each 60w max.

SMALL WALL-LANTERN

P560014-020 Antique Bronze
P560014-031 Black
 6-1/4" W., 13-1/4" ht.
 Extends 8-5/8". H/CTR 5-3/4".
 One medium base lamp,
 100w max.

MEDIUM WALL-LANTERN

P560015-020 Antique Bronze
P560015-031 Black
 8-1/4" W., 17-3/4" ht.
 Extends 11-3/8". H/CTR 10-1/8".
 One medium base lamp,
 100w max.

LARGE WALL-LANTERN

P560016-020 Antique Bronze
P560016-031 Black
 10-3/8" W., 21-3/4" ht.
 Extends 13-5/8". H/CTR 10".
 Three candelabra base lamps,
 each 60w max.

*EXTRA-LARGE
 WALL-LANTERN*

P560017-020 Antique Bronze
P560017-031 Black
 10-3/8" W., 30-1/2" ht.
 Extends 13-1/4". H/CTR 14-3/4".
 Three candelabra base lamps,
 each 60w max.



P560017-020



P560017-031



P540002-031

CREIGHTON

Creighton features clear water glass with Antique Bronze or Black finish options. The frame's linear details are riveted to enhance mechanical detailing of the fixture. Wall, post and hanging lantern options available.



P550009-020



P560031-031



P560031-020



P560032-031



P560032-020



P560033-031



P560033-020



P540009-031



P540009-020



P550009-020



P550009-031

FINISHES

- Antique Bronze - 020
- Black - 031

POST LANTERN

P540009-020 Antique Bronze
P540009-031 Black
 10-1/2" dia., 21-3/4" ht.
 Fits 3" post (order separately).
 One medium base lamp,
 100w max.

HANGING LANTERN

P550009-020 Antique Bronze
P550009-031 Black
 10-1/2" dia., 21-5/8" ht.
 Overall ht. w/chain 96-1/2"; wire 10'.
 One medium base lamp,
 100w max.

SMALL WALL-LANTERN

P560031-020 Antique Bronze
P560031-031 Black
 6" W., 11-1/2" ht.
 Extends 7-1/4". H/CTR 2-3/8".
 One medium base lamp,
 100w max.

MEDIUM WALL-LANTERN

P560032-020 Antique Bronze
P560032-031 Black
 8-3/8" W., 15-3/4" ht.
 Extends 9-3/8". H/CTR 3".
 One medium base lamp,
 100w max.

LARGE WALL-LANTERN

P560033-020 Antique Bronze
P560033-031 Black
 10-1/2" W., 19-1/4" ht.
 Extends 11-1/8". H/CTR 3".
 One medium base lamp,
 100w max.

UNION SQUARE

Union Square features a reproduction gas lantern inspiration. A Stainless Steel finish complements the natural polished material and clear flat glass panels. Mechanical details – such as exaggerated knobs – provide character to the form. Open bottom on wall lanterns provides easy access for cleaning and relamping.



ALSO AVAILABLE IN

Bath Collections, page 194



P560005-135



P560004-135



P560005-135



P560006-135



P550018-135



P550007-135

FINISH

- Stainless Steel - 135

FLUSH MOUNT

P550007-135 Stainless Steel
12-3/8" sq., 5-1/2" ht.
Two medium base lamps,
each 60w max.

SMALL WALL-LANTERN

P560004-135 Stainless Steel
6-1/2" W., 15-7/8" ht.
Extends 5-1/2". H/CTR 6-1/4".
One medium base lamp,
100w max.

MEDIUM WALL-LANTERN

P560005-135 Stainless Steel
7-7/8" W., 19-3/8" ht.
Extends 6-1/2". H/CTR 7-3/4".
One medium base lamp,
100w max.

LARGE WALL-LANTERN

P560006-135 Stainless Steel
9-3/4" W., 23-5/8" ht.
Extends 8". H/CTR 9-5/8".
One medium base lamp,
100w max.


OUTDOOR HANGING LANTERN

P550018-135 Stainless Steel
7" sq., 27-3/8" ht.
Overall ht. w/chain 102-1/2", wire 10'.
One medium base lamp,
100w max.

*Fixtures shown with P7827-01
vintage lamps*

GIBBES STREET

Elongated frames capture the romantic charm of vintage gas lanterns. Inspired by a stroll down a Charlestonian street bearing the same name, the Gibbs Street outdoor lantern collection features clear beveled glass and an Antique Bronze finish. Wall, post and hanging lanterns complete the family.



P550004-020
shown with P7826-01
vintage lamp



P560021-020
shown with P7827-01
vintage lamp



P560022-020
shown with P7826-01
vintage lamp



P560023-020
shown with P7826-01
vintage lamp



P550004-020
shown with P7826-01
vintage lamp



P540004-020
shown with P7826-01
vintage lamp

FINISH

● Antique Bronze - 020

POST LANTERN

P540004-020 Antique Bronze
9-1/2" dia., 26-7/8" ht.
Fits 3" post (order separately).
Three candelabra base lamps,
each 60w max.

HANGING LANTERN

P550004-020 Antique Bronze
9-1/2" dia., 23-3/4" ht.
Overall ht. w/chain 99"; wire 10'.
Three candelabra base lamps,
each 60w max.

SMALL WALL LANTERN

P560021-020 Antique Bronze
5-1/2" W., 15-1/8" ht.
Extends 7". H/CTR 5-7/8".
One medium base lamp,
100w max.

MEDIUM WALL LANTERN

P560022-020 Antique Bronze
7" W., 21-3/4" ht.
Extends 8-3/4". H/CTR 8-3/8".
Two candelabra base lamps,
each 60w max.

LARGE WALL LANTERN

P560023-020 Antique Bronze
9-1/2" W., 30-5/8" ht.
Extends 11-1/4". H/CTR 10-3/4".
Three candelabra base lamps,
each 60w max.

SANTEE

A classic colonial wall lantern with contemporary touches describes Santee. Featuring a geometric frame and graphic handle, the wider beveled glass offers more refraction – and visual interest – than typical lantern designs. Choose from a Black frame with stainless steel candle option or an Antique Bronze frame with painted brass candle option.



P560003-020



P560002-020



P560002-031

FINISHES

- Antique Bronze - 020
- Black - 031

SMALL WALL LANTERN

P560002-020 Antique Bronze
P560002-031 Black
8" W., 15-1/4" ht.
Extends 5-3/4". H/CTR 8-3/4".
Two candelabra base lamps,
each 60w max.

LARGE WALL LANTERN

P560003-020 Antique Bronze
P560003-031 Black
9-1/2" W., 19-5/8" ht.
Extends 6-1/2". H/CTR 11-3/8".
Three candelabra base lamps,
each 60w max.

*Fixtures shown with P7826-01
vintage lamps*




P560003-020



P560003-031

PATEWOOD NEW

Patewood lanterns have a modern shadowbox housing in a sleek Black finish constructed from durable stainless steel. The pillar candle style diffusers provide crisp illumination for a pleasing complement to your home's exterior.



P550024-031



FINISH

● Black - 031

POST LANTERN

P540013-031 Black
Fits 3" post (order separately).
7" W., 19-3/8" ht.
One medium base lamp,
100w max.

HANGING LANTERN

P550013-031 Black
5-1/2" W., 15-1/8" ht.
Overall ht. w/stem 81", wire 10'.
One medium base lamp,
100w max.

HANGING LANTERN

P550024-031 Black
7 W., 18" ht.
Overall ht. w/stem 84, wire 10'.
One medium base lamp,
100w max.

SMALL WALL LANTERN

P560039-031 Black
4-1/2" W., 12" ht.
Extends 5-3/8". H/CTR 8-5/8".
One medium base lamp,
75w max.

MEDIUM WALL LANTERN

P560040-031 Black
5-11/16" W., 14-1/2" ht.
Extends 6-1/2". H/CTR 10".
One medium base lamp,
100w max.

LARGE WALL LANTERN

P560041-031 Black
7" W., 17-3/8" ht.
Extends 7-3/4". H/CTR 11-7/8".
One medium base lamp,
100w max.

KIAWAH

Seeded glass panels and traditional detailing combine to create a soft and updated lantern design. Hinged door for easy relamping is available for post, hanging and medium, large and extra large wall lanterns.



P550001-031



P560010-031



P550001-031



P560011-031



P560012-031



P560013-031



P540001-031

FINISH

- Black - 031

POST LANTERN

P540001-031 Black
9-1/2" sq., 20-7/8" ht.
Fits 3" post (order separately).
Three candelabra base lamps,
each 60w max.

HANGING LANTERN

P550001-031 Black
9-1/2" sq., 19-5/8" ht.
Overall ht. w/chain 94-1/2"; wire 10'.
Three candelabra base lamps,
each 60w max.

SMALL WALL LANTERN

P560010-031 Black
5-5/8" W., 12-7/8" ht.
Extends 6-3/8". H/CTR 5-3/8".
One medium base lamp,
100w max.

MEDIUM WALL LANTERN

P560011-031 Black
7-1/2" W., 21-7/8" ht.
Extends 8-3/8". H/CTR 8-1/4".
Two candelabra base lamps,
each 60w max.

LARGE WALL LANTERN

P560012-031 Black
9-1/2" W., 27-1/4" ht.
Extends 10-1/4". H/CTR 10".
Three candelabra base lamps,
each 60w max.

*EXTRA-LARGE
WALL LANTERN*

P560013-031 Black
12-1/2" W., 34-1/2" ht.
Extends 13-1/2". H/CTR 10-3/4".
Three candelabra base lamps,
each 60w max.

TWAIN

Featuring an updated prairie style, Twain's lantern collection offers visual interest for a variety of home exteriors. Solid glass with the center sand blasted, is divided by the frames vertical lines.



P550000-020



P560007-020



P560008-020



P560009-020



P550000-020



P540000-020

FINISH

- Antique Bronze - 020

POST LANTERN

P540000-020 Antique Bronze
7-3/4" sq., 16" ht.
Fits 3" post (order separately).
One medium base lamp,
100w max.

HANGING LANTERN

P550000-020 Antique Bronze
7-3/4" sq., 13-3/4" ht.
Overall ht. w/chain 88-1/2"; wire 10'.
One medium base lamp,
100w max.

SMALL WALL LANTERN

P560007-020 Antique Bronze
5-3/4" W., 10-1/4" ht.
Extends 6-3/4". H/CTR 2-3/8".
One medium base lamp,
100w max.

MEDIUM WALL LANTERN

P560008-020 Antique Bronze
7-3/4" W., 13-1/2" ht.
Extends 8-7/8". H/CTR 2-3/4".
One medium base lamp,
100w max.

LARGE WALL LANTERN

P560009-020 Antique Bronze
9-1/2" W., 16-1/2" ht.
Extends 10-3/4". H/CTR 3-1/4".
One medium base lamp,
100w max.

PRODUCT INDEX

P2000

| | |
|-------|---------|
| P2154 | 209 |
| P2155 | 209 |
| P2156 | 209 |
| P2157 | 209 |
| P2193 | 227 |
| P2194 | 227 |
| P2195 | 227 |
| P2196 | 227 |
| P2325 | 61 |
| P2326 | 59 |
| P2850 | 79, 199 |
| P2854 | 199 |
| P2856 | 199 |
| P2857 | 199 |

P3000

| | |
|---------|---------------|
| P300000 | 211 |
| P300001 | 211 |
| P300002 | 211 |
| P300003 | 211 |
| P300004 | 117, 119, 213 |
| P300005 | 213 |
| P300006 | 213 |
| P300007 | 213 |
| P300008 | 91, 93, 207 |
| P300009 | 207 |
| P300010 | 207 |
| P300011 | 207 |
| P300012 | 219, 220, 221 |
| P300013 | 219, 220, 221 |
| P300014 | 219, 220, 221 |
| P300015 | 219, 220, 221 |
| P300016 | 217 |
| P300017 | 217 |
| P300018 | 217 |
| P300019 | 217 |
| P300020 | 75, 77, 205 |
| P300021 | 205 |
| P300022 | 205 |
| P300023 | 205 |
| P300024 | 223, 224, 225 |
| P300025 | 223, 224, 225 |
| P300026 | 223, 224, 225 |
| P300027 | 223, 224, 225 |
| P300035 | 107, 201 |
| P300036 | 201 |
| P300037 | 201 |
| P300038 | 201 |
| P300040 | 75, 77 |
| P300061 | 191 |
| P300062 | 191 |
| P300063 | 189 |
| P300064 | 189 |
| P300065 | 189 |
| P300100 | 215 |
| P300101 | 215 |
| P300102 | 215 |
| P300103 | 215 |
| P300105 | 63, 65, 193 |
| P300106 | 193 |
| P300107 | 193 |
| P300108 | 47, 203 |

| | |
|---------|----------|
| P300109 | 203 |
| P300110 | 203 |
| P300111 | 203 |
| P300112 | 197 |
| P300113 | 197 |
| P300114 | 197 |
| P300115 | 197 |
| P300135 | 195 |
| P300136 | 195 |
| P350021 | 121 |
| P350027 | 135 |
| P350028 | 85 |
| P350029 | 113 |
| P350030 | 52 |
| P350031 | 57 |
| P350032 | 117, 119 |
| P350034 | 109, 111 |
| P350036 | 91, 93 |
| P350040 | 75, 77 |
| P350041 | 95 |
| P350050 | 107 |
| P350058 | 60 |
| P350090 | 63, 65 |
| P350092 | 115 |
| P350095 | 123 |
| P350102 | 67, 69 |
| P350105 | 75, 77 |
| P350106 | 49 |
| P3598 | 133 |
| P3601 | 133 |
| P3604 | 137 |
| P3868 | 139 |

P4000

| | |
|---------|----------|
| P400000 | 169 |
| P400002 | 131 |
| P400003 | 131 |
| P400004 | 51 |
| P400005 | 52 |
| P400006 | 52 |
| P400007 | 57 |
| P400008 | 117, 119 |
| P400009 | 117, 119 |
| P400010 | 117, 119 |
| P400011 | 109, 111 |
| P400012 | 109, 111 |
| P400013 | 109, 111 |
| P400014 | 109, 111 |
| P400015 | 91, 93 |
| P400016 | 91, 93 |
| P400017 | 91, 93 |
| P400018 | 107 |
| P400019 | 81 |
| P400020 | 81 |
| P400021 | 75, 77 |
| P400022 | 75, 77 |
| P400023 | 75, 77 |
| P400024 | 87, 89 |
| P400025 | 87, 89 |
| P400026 | 87, 89 |
| P400027 | 95 |
| P400028 | 95 |
| P400037 | 107 |
| P400038 | 107 |
| P400040 | 83 |
| P400041 | 83 |
| P400045 | 121 |
| P400046 | 121 |
| P400049 | 113 |
| P400051 | 97 |
| P400068 | 55 |
| P400069 | 55 |
| P400070 | 55 |
| P400071 | 47 |
| P400072 | 47 |
| P400075 | 115 |
| P400076 | 115 |
| P400077 | 73 |
| P400078 | 49 |
| P400079 | 49 |

P5000

| | | | | | | | |
|---------|---------|---------|----------|---------|---------|---------|-----|
| P400080 | 99, 101 | P500000 | 169 | P500084 | 73 | P5345 | 141 |
| P400081 | 99, 101 | P500003 | 85 | P500085 | 49 | P5346 | 59 |
| P400082 | 99, 101 | P500004 | 85 | P500086 | 49 | P540000 | 259 |
| P400083 | 99, 101 | P500005 | 57 | P500088 | 99, 101 | P540001 | 257 |
| P400084 | 73 | P500006 | 117, 119 | P500089 | 99, 101 | P540002 | 245 |
| P400089 | 123 | P500007 | 109, 111 | P500091 | 55 | P540003 | 243 |
| P400090 | 123 | P500010 | 97 | P500095 | 63, 65 | P540004 | 251 |
| P400091 | 123 | P500011 | 97 | P500096 | 73 | P540009 | 247 |
| P400092 | 123 | P500012 | 97 | P500097 | 125 | P540013 | 255 |
| P400098 | 45 | P500013 | 163 | P500098 | 161 | P540026 | 235 |
| P400099 | 45 | P500014 | 163 | P500101 | 123 | P540027 | 237 |
| P400100 | 49 | P500015 | 81 | P500105 | 45 | P550000 | 259 |
| P400101 | 60 | P500016 | 135 | P500106 | 45 | P550001 | 257 |
| P400105 | 67, 69 | P500017 | 135 | P500107 | 45 | P550002 | 245 |
| P400106 | 67, 69 | P500020 | 95 | P500108 | 45 | P550003 | 243 |
| P400108 | 71 | P500024 | 107 | P500109 | 60 | P550004 | 251 |
| P400109 | 71 | P500025 | 149 | P500115 | 67, 69 | P550007 | 249 |
| P400116 | 63, 65 | P500026 | 149 | P500116 | 67, 69 | P550009 | 247 |
| P400117 | 87, 89 | P500031 | 159 | P500117 | 67, 69 | P550013 | 255 |
| P4755 | 79 | P500032 | 161 | P500118 | 145 | P550024 | 255 |
| P4756 | 79 | P500033 | 161 | P500119 | 175 | P550026 | 235 |
| P4760 | 103 | P500036 | 125 | P500120 | 175 | P550027 | 237 |
| P4761 | 103 | P500037 | 125 | P500123 | 173 | P560002 | 253 |
| P4763 | 103 | P500038 | 127 | P500124 | 173 | P560003 | 253 |
| P4766 | 105 | P500039 | 127 | P5015 | 137 | P560004 | 249 |
| P4767 | 105 | P500040 | 127 | P5021 | 137 | P560005 | 249 |
| | | P500042 | 131 | P5073 | 133 | P560006 | 249 |
| | | P500043 | 113 | P5309 | 157 | P560007 | 259 |
| | | P500044 | 177 | P5311 | 157 | P560008 | 259 |
| | | P500045 | 177 | P5317 | 103 | P560009 | 259 |
| | | P500046 | 147 | P5318 | 105 | P560010 | 257 |
| | | P500047 | 147 | P5319 | 139 | P560011 | 257 |
| | | P500048 | 129 | P5320 | 61 | P560012 | 257 |
| | | P500049 | 129 | P5321 | 59 | P560013 | 257 |
| | | P500060 | 177 | P5322 | 139 | P560014 | 245 |
| | | P500063 | 153 | P5324 | 167 | P560015 | 245 |
| | | P500064 | 155 | P5325 | 167 | P560016 | 245 |
| | | P500073 | 63, 65 | P5329 | 171 | P560017 | 245 |
| | | P500074 | 63, 65 | P5332 | 151 | P560018 | 243 |
| | | P500075 | 47 | P5333 | 151 | P560019 | 243 |
| | | P500076 | 47 | P5334 | 151 | P560020 | 243 |
| | | P500077 | 47 | P5335 | 143 | P560021 | 251 |
| | | P500080 | 115 | P5336 | 143 | P560022 | 251 |
| | | P500081 | 115 | P5337 | 165 | P560023 | 251 |
| | | P500082 | 73 | P5338 | 165 | P560031 | 247 |
| | | P500083 | 73 | P5344 | 141 | P560032 | 247 |

PRODUCT INDEX *(cont'd)*

P5000 *(cont'd)*

| | |
|---------|-----|
| P560033 | 247 |
| P560039 | 255 |
| P560040 | 255 |
| P560041 | 255 |
| P560068 | 235 |
| P560069 | 235 |
| P560070 | 235 |
| P560074 | 237 |
| P560075 | 237 |
| P560076 | 237 |

P6000

| | |
|-------|-----|
| P6080 | 231 |
| P6438 | 241 |
| P6439 | 229 |
| P6440 | 239 |
| P6441 | 233 |
| P6442 | 231 |
| P6538 | 241 |
| P6539 | 229 |
| P6540 | 239 |
| P6541 | 233 |
| P6542 | 231 |
| P6619 | 241 |
| P6620 | 241 |
| P6621 | 241 |
| P6622 | 241 |
| P6626 | 229 |
| P6627 | 229 |
| P6628 | 229 |
| P6629 | 229 |
| P6630 | 239 |
| P6631 | 239 |
| P6632 | 239 |
| P6633 | 239 |
| P6634 | 233 |
| P6635 | 233 |
| P6636 | 233 |
| P6637 | 233 |
| P6638 | 231 |
| P6639 | 231 |
| P6640 | 231 |

P7000

| | |
|---------|----------|
| P710001 | 85 |
| P710002 | 131 |
| P710003 | 52 |
| P710004 | 57 |
| P710005 | 109, 111 |
| P710006 | 81 |
| P710007 | 135 |
| P710008 | 95 |
| P710013 | 113 |
| P710016 | 181 |
| P710017 | 187 |
| P710018 | 185 |
| P710019 | 185 |
| P710021 | 129 |
| P710022 | 179 |
| P710023 | 179 |
| P710024 | 179 |
| P710025 | 183 |
| P710027 | 71 |
| P710029 | 115 |
| P710030 | 49 |
| P710032 | 55 |
| P710034 | 123 |
| P710037 | 45 |
| P710038 | 195 |
| P710043 | 67, 69 |
| P7117 | 141 |
| P7125 | 141 |
| P7198 | 61 |

P8000

| | |
|---------|-------------|
| P860000 | 51 |
| P860001 | 51 |
| P860002 | 91, 93, 207 |
| P860003 | 91, 93, 207 |

ICON KEY



Products identified as Energy Efficient have been designed to utilize light sources that consume less power than equivalent traditional incandescent sources.



Products referencing this logo meet the energy efficiency requirements for light fixtures set forth in ENERGY STAR® product specifications. Please refer to www.energystar.gov for specific product qualifications and list of certified products.



This marking indicates fixtures that have an integrated LED or replaceable LED module that has been tested and listed in the California Appliance Database. Check for certified lamps, fixtures or LED light engines by searching the MAEDBS database. Go to cacertappliances.energy.ca.gov



Table 150.0A defines products that do not have to meet JA8 and can be used to comply with 2016 Title 24. The most common types include:

- Pin-based linear or compact fluorescent light sources using electronic ballasts
- GU-24 sockets containing light sources other than LEDs
- Inseparable SSL luminaires that are installed outdoors

Every effort has been made to ensure the accuracy of information in this catalog. Progress Lighting reserves the right to make product changes from time to time, without prior notification, which may change the information provided in this catalog. Errors brought to our attention will be corrected in subsequent issues.

UL, CSA, or ETL Listed or Classified unless otherwise noted.

Bulbs not included with fixtures unless specified. Specifications subject to change without notice.

Metal finishes not specified as "solid" have quality plated or painted finishes.

Finish representations are high resolution digital reproductions, and, while every effort has been made to render colors accurately, they may vary slightly from the actual product, especially hand-painted finishes, due to the nature of hand craftsmanship.

©Progress Lighting 2018

All rights reserved.

International copyright secured.



701 Millennium Boulevard
Greenville, South Carolina
29607



