

PRO  
SERIES

**C-LITE™**  
LED LIGHTING BY CREE

**CREE** 



**C-Lite™ Products,  
Cree Pro Series Lamps and Downlights**



## C-LITE™ - YOUR TRUSTED VALUE BRAND.

C-Lite™ LED Lighting by Cree offers a broad range of reliable, easy to install LED lighting products with all the options you need. All products meet Cree’s rigorous testing standards in order to provide superior quality and dependability, and are fully backed by Cree.

### SIMPLE

Our mission is simple: provide high performance, go-to LED lighting at incredible value. Contractors have enough to worry about—C-Lite™ products make lighting projects one less hurdle in a day full of them.

### EASY

From easy installation to making sure our products are always in stock, easy to find and ready to work, we make jobs of all sizes quick, easy and painless. C-Lite™ LED Lighting by Cree is your no hassle, “hey, that was easy” choice.

### QUALITY

Cree won’t put their name on just any box. Engineered to deliver great energy savings and powerful performance, C-Lite™ LED Lighting by Cree is backed by a great warranty and Cree’s world-class live customer support. You can relax knowing that with this, Cree has got your back.



## PRODUCTS

### C-LITE™ - LED OUTDOOR

LED Area Lights .....	4
Dusk to Dawn LED Area Lights .....	4
Shoebox LED Area Lights .....	5
LED Area Light Accessories .....	6
LED Canopy Lights .....	7
Compact LED Floodlights .....	8
High Performance LED Floodlights & Accessories .....	9
LED Wall Mounts .....	10
Slimline LED Wall Packs .....	11
Slimline LED Wall Pack Accessories .....	12
LED Wall Packs (Non Cutoff) .....	13
LED Wall Pack (Full Cutoff) & Accessories .....	14
LED Vapor Tights & Accessories .....	15

### LED INDOOR

C-Lite™ LED Downlights .....	16
Cree® LED Downlights .....	17
Cree® LED Downlight Accessories .....	18
Cree® LED Surface Mount Disk Lights & Accessories .....	19
C-Lite™ LED Flat Panel Troffers .....	20
C-Lite™ LED Strips & Wraps .....	21
C-Lite™ LED Round Low Bays .....	22
C-Lite™ LED Linear High Bays .....	23
C-Lite™ LED High & Low Bay Accessories .....	24
C-Lite™ General LED Accessories .....	25

### LED LAMPS

C-Lite™ LED Lamps .....	26
Cree® Professional Series LED Lamps .....	27

# Cree® Professional Series LED Lamps & LED Downlights

## LIGHT YOUR SPACE LIKE A PRO.

The NEW Cree® PRO Series LED lamps and LED downlights feature a remarkable combination of performance and quality, designed exclusively for spec-grade projects. They feature beautiful, high-CRI light that provides exceptional color quality, making colors appear vibrant, rich and natural. These lamps and downlights are backed by a no-hassle warranty—making Cree the easy choice for your LED lamp and downlight needs.

## SERIES FEATURES

- Exceptional 90+ CRI color consistency
- Exceeds ENERGY STAR® rated lifetime requirements for most products, up to 25,000 hours
- Meets CEC Title 20/Title 24 JA-8 performance requirements
- Enclosure-rated lamps for use in more applications
- Higher lumen lamps and downlights offer more light for higher ceilings
- Shatterproof lamps
- Smooth, superior dimmability
- No-hassle 5-year limited warranty



All Professional Series lamps and downlights offered in single cartons.



\* See [lighting.cree.com/warranty](http://lighting.cree.com/warranty) for details



LED Area Light (4LD)



LED Area Light (2LD)

## LED AREA LIGHTS

### Stylish Modern Design, Type III Optimized Distribution

- Category: LED Outdoor Area Light
- CRI: >70
- Location Type: Wet
- Voltage: 120-277V
- High LPW: up to 103
- Watts: 117 to 228
- Non-Dimmable
- Cree LEDs, quality driver

Item	SKU	Replaces	CCT	Lumens	Finish Color
LED Area Light	C-AR-A-2LD-12L-40K-DB	250W PSMH	4000K	12,400	Dark Bronze
LED Area Light	C-AR-A-2LD-12L-50K-DB	250W PSMH	5000K	12,200	Dark Bronze
LED Area Light	C-AR-A-4LD-23L-40K-DB	400W PSMH	4000K	23,100	Dark Bronze
LED Area Light	C-AR-A-4LD-23L-50K-DB	400W PSMH	5000K	22,800	Dark Bronze

## DUSK TO DAWN LED AREA LIGHTS

### Versatile, Reliable, Efficient



LED Dusk to Dawn (3L)

- Category: LED Outdoor Area Light
- CRI: >70
- Location Type: Wet
- Voltage: 120-277V
- Watts: 23
- Non-Dimmable
- Finish Color: Gray

Item	SKU	Replaces	CCT	Lumens	Size
LED Area Light	C-AR-A-DD-3L-50K-GR	70W MH	5000K	2,800	12" L x 7-12" W x 6-3/4" H

**NOTE:** For Area Light accessories refer to Page 6, for General LED lighting accessories refer to page 25

\*See [lighting.cree.com/warranty](http://lighting.cree.com/warranty) for details



LED Shoebox Area Light

## SHOEBOX LED AREA LIGHTS

### Stylish, Modern Design; Type III, V and VII Optimized Distributions

- Category: LED Outdoor Area Light
- CRI: >70
- Location Type: Wet
- Voltage: 120-277V
- Cree LEDs, quality driver
- High LPW: up to 143
- Watts: 119
- Non-Dimmable
- Finish Color: Dark Bronze

Item	SKU	Replaces	CCT	Lumens	Size
LED Area Light	C-AR-A-SQT3-16L-40K-DB	320W PSMH / 400W MH	4000K	16,100	16-1/5" x 16-1/5"
LED Area Light	C-AR-A-SQT3-17L-50K-DB	320W PSMH / 400W MH	5000K	17,100	16-1/5" x 16-1/5"
LED Area Light	C-AR-A-SQT5-15L-50K-DB	320W PSMH / 400W MH	5000K	15,200	16-1/5" x 16-1/5"
LED Area Light	C-AR-A-SQT5-16L-40K-DB	320W PSMH / 400W MH	4000K	16,100	16-1/5" x 16-1/5"
LED Area Light	C-AR-A-SQT7-17L-50K-DB	320W PSMH / 400W MH	5000K	16,900	16-1/5" x 16-1/5"
LED Area Light	C-AR-A-SQT7-17L-40K-DB	320W PSMH / 400W MH	4000K	16,900	16-1/5" x 16-1/5"

**NOTE:** For Area Light accessories refer to Page 6, for General LED lighting accessories refer to page 25

\*See [lighting.cree.com/warranty](http://lighting.cree.com/warranty) for details



LED Adjustable U-Bracket



LED 6" Mounting Arm



LED Mount Slipfitter 2in



LED Mounting Arm Kit



LED Photocell 120V/208V/240V/277V

## LED AREA LIGHT ACCESSORIES

### Accessories for C-Lite™ Area Lights

• Category: LED Outdoor Accessories

Product/Item	SKU	Finish Color	Size/Fits
LED Adjustable U-Bracket	C-ACC-A-AUB-2X5X6-DB	Dark Bronze	Fits C-AR-A-2LD Series, 2" X 5" X 6"
LED 6" Mounting Arm	C-ACC-A-MTARM-6IN-DB	Dark Bronze	6in, Fits C-AR-A-2LD, C-AR-A-4LD Series
LED Adjustable U-Bracket	C-ACC-A-AUB-3X5X5-DB	Dark Bronze	Fits C-AR-A-4LD Series, 3" X 5" X 5"
LED Mount Slipfitter 2"	C-ACC-A-MTSL-2IN-DB	Dark Bronze	2in, Fits C-AR-A-2LD, C-AR-A-4LD, C-AR-A-SQT5, C-AR-A-SQT7 Series
LED 6" Mounting Arm	C-ACC-A-SBMTARM-6IN-DB	Dark Bronze	Fits C-AR-A-SQT3, C-AR-A-SQT5, C-AR-A-SQT7 Series
LED Mounting Arm Kit	C-ACC-A-SMDDPOLE-GR	Gray	For C-AR-A-DD-3L Series
LED Adjustable U-Bracket	C-ACC-A-AUB-DB	Dark Bronze	Fits C-AR-A-SQT3, AR-A-SQT5, C-AR-A-SQT7 Series
LED Photocell 120V	C-ACC-A-PCELL-LV	-	120V, Fits C-AR-A-2LD, C-AR-A-4LD, C-AR-A-SQT3, C-AR-A-SQT5, C-AR-A-SQT7 Series
LED Photocell 208-277V	C-ACC-A-PCELL-HV-TL	-	208-277V, Fits C-AR-A-2LD, C-AR-A-4LD, C-AR-A-SQT3, C-AR-A-SQT5, C-AR-A-SQT7 Series

\*See [lighting.cree.com/warranty](http://lighting.cree.com/warranty) for details



Square Canopy


## LED CANOPY LIGHTS

### Traditional Style; Easy Installation

- Category: LED Outdoor Canopy
- CRI: >70
- Location Type: Wet
- Voltage: 120-277V
- High LPW: Up to 136
- Watts: 28 to 95
- Non-Dimmable
- Cree LEDs, quality driver

Item	SKU	Replaces	CCT	Lumens	Finish Color	Size/Fits
Square LED Canopy	C-CP-A-SQ-30L-40K-DB	70W PSMH	4000K	3,000	Dark Bronze	Hole Size: 9-7/8" x 9-7/8"
Square LED Canopy	C-CP-A-SQ-30L-40K-WH	70W PSMH	4000K	3,000	White	Hole Size: 9-7/8" x 9-7/8"
Square LED Canopy	C-CP-A-SQ-30L-50K-DB	70W PSMH	5000K	3,000	Dark Bronze	Hole Size: 9-7/8" x 9-7/8"
Square LED Canopy	C-CP-A-SQ-30L-50K-WH	70W PSMH	5000K	3,000	White	Hole Size: 9-7/8" x 9-7/8"
Square LED Canopy	C-CP-A-SQ-49L-40K-DB	100W PSMH	4000K	4,900	Dark Bronze	Hole Size: 9-7/8" x 9-7/8"
Square LED Canopy	C-CP-A-SQ-49L-40K-WH	100W PSMH	4000K	4,900	White	Hole Size: 9-7/8" x 9-7/8"
Square LED Canopy	C-CP-A-SQ-49L-50K-DB	100W PSMH	5000K	4,900	Dark Bronze	Hole Size: 9-7/8" x 9-7/8"
Square LED Canopy	C-CP-A-SQ-49L-50K-WH	100W PSMH	5000K	4,900	White	Hole Size: 9-7/8" x 9-7/8"
Square LED Canopy	C-CP-A-SQ-79L-40K-DB	150W PSMH 175W MH 200W MH	4000K	7,900	Dark Bronze	Hole Size: 13-1/3" x 13-1/3"
Square LED Canopy	C-CP-A-SQ-79L-40K-WH	150W PSMH 175W MH 200W MH	4000K	7,900	White	Hole Size: 13-1/3" x 13-1/3"
Square LED Canopy	C-CP-A-SQ-79L-50K-DB	150W PSMH 175W MH 200W MH	5000K	7,900	Dark Bronze	Hole Size: 13-1/3" x 13-1/3"
Square LED Canopy	C-CP-A-SQ-79L-50K-WH	150W PSMH 175W MH 200W MH	5000K	7,900	White	Hole Size: 13-1/3" x 13-1/3"
Square LED Canopy	C-CP-A-SQ-120L-40K-DB	250W PSMH	4000K	12,000	Dark Bronze	Hole Size: 14" x 14"
Square LED Canopy	C-CP-A-SQ-120L-40K-WH	250W PSMH	4000K	12,000	White	Hole Size: 14" x 14"
Square LED Canopy	C-CP-A-SQ-120L-50K-DB	250W PSMH	5000K	12,000	Dark Bronze	Hole Size: 14" x 14"
Square LED Canopy	C-CP-A-SQ-120L-50K-WH	250W PSMH	5000K	12,000	White	Hole Size: 14" x 14"

\*See [lighting.cree.com/warranty](http://lighting.cree.com/warranty) for details



Premium LED Compact Flood



Premium LED Directional Flood

## COMPACT LED FLOODLIGHTS

High Quality; Easy Installation; 5 Year Limited Warranty\*

- Category: LED Outdoor Floodlights/Spot Lights
- CRI: >70
- Location Type: Wet
- Voltage: 120-277V
- Non-Dimmable
- High LPW: Up to 106
- Watts: 9 to 35
- Cree LEDs, quality driver

Item	SKU	Replaces	CCT	Lumens	Finish Color	Size/Fits
Premium LED Compact Flood	C-FL-A-RC-2L-40K-DB	50W MH	4000K	1,600	Dark Bronze	4-3/4" H x 6-1/8" W x 4-3/4" D
Premium LED Compact Flood	C-FL-A-RC-2L-40K-WH	50W MH	4000K	1,600	White	4-3/4" H x 6-1/8" W x 4-3/4" D
Premium LED Compact Flood	C-FL-A-RC-3L-40K-DB	100W PSMH	4000K	2,900	Dark Bronze	6" H x 7-3/4" W x 4-3/4" D
Premium LED Compact Flood	C-FL-A-RC-3L-40K-WH	100W PSMH	4000K	2,900	White	6" H x 7-3/4" W x 4-3/4" D
Premium LED Compact Flood	C-FL-A-RC-3L-50K-DB	100W PSMH	5000K	2,900	Dark Bronze	6" H x 7-3/4" W x 4-3/4" D
Premium LED Compact Flood	C-FL-A-RC-3L-50K-WH	100W PSMH	5000K	2,900	White	6" H x 7-3/4" W x 4-3/4" D
Premium LED Directional Flood	C-FL-A-RDC-1L-40K-BK	50W Halogen	4000K	700	Black	4" H x 4" W x 4-5/8" D
Premium LED Directional Flood	C-FL-A-RDC-1L-40K-WH	50W Halogen	4000K	700	White	4" H x 4" W x 4-5/8" D
Premium LED Directional Flood	C-FL-A-RDW-3L-40K-DB	100W PSMH / 70W MH	4000K	3,200	Dark Bronze	7-2/5" H x 6" W x 8-1/2" D
Premium LED Directional Flood	C-FL-A-RDW-3L-50K-DB	100W PSMH / 70W MH	5000K	3,400	Dark Bronze	7-2/5" H x 6" W x 8-1/2" D
Premium LED Directional Flood	C-FL-A-RDM-3L-40K-DB	100W PSMH / 70W MH	4000K	3,500	Dark Bronze	7-2/5" H x 6" W x 8-1/2" D
Premium LED Directional Flood	C-FL-A-RDM-4L-50K-DB	100W PSMH / 70W MH	5000K	3,800	Dark Bronze	7-2/5" H x 6" W x 8-1/2" D

\*See [lighting.cree.com/warranty](http://lighting.cree.com/warranty) for details



## HIGH PERFORMANCE LED FLOODLIGHTS & ACCESSORIES

High Quality; Easy Installation; 5 Year Limited Warranty\*

- Category: LED Outdoor Floodlights & Accessories
- CRI: >70
- Location Type: Wet
- Voltage: 120-277V
- Non-Dimmable
- Finish Color: Dark Bronze
- High LPW: Up to 118
- Watts: 74 to 234



Premium LED Floodlight-Large



High-Output LED Floodlight



Premium LED Floodlight-Small



LED Photocell 120V-277V

Item	SKU	Replaces	CCT	Lumens	Size/Fits
Premium LED Floodlight-Small	C-FL-A-RTF1-8L-40K-DB	150W PSMH / 175W MH	4000K	8,100	11" H x 9-4/9"W x 5-1/2" D
Premium LED Floodlight-Small	C-FL-A-RTF1-7L-50K-DB	150W PSMH / 175W MH	5000K	7,400	11" H x 9-4/9" W x 5-1/2" D
Premium LED Floodlight-Small	C-FL-A-RTS1-8L-40K-DB	150W PSMH / 175W MH	4000K	8,000	11" H x 9-4/9" W x 5-1/2" D
Premium LED Floodlight-Small	C-FL-A-RTS1-7L-50K-DB	150W PSMH / 175W MH	5000K	7,300	11" H x 9-4/9" W x 5-1/2" D
Premium LED Floodlight-Large	C-FL-A-RTF2-12L-40K-DB	250W PSMH	4000K	12,300	14-5/8" H x 12-3/4" W x 7-3/8" D
Premium LED Floodlight-Large	C-FL-A-RTF2-12L-50K-DB	250W PSMH	5000K	12,400	14-5/8" H x 12-3/4" W x 7-3/8" D
Premium LED Floodlight-Large	C-FL-A-RTS2-13L-40K-DB	250W PSMH	4000K	13,600	14-5/8" H x 12-3/4" W x 7-3/8" D
Premium LED Floodlight-Large	C-FL-A-RTS2-14L-50K-DB	250W PSMH	5000K	13,900	14-5/8" H x 12-3/4" W x 7-3/8" D
High-Output LED Floodlight	C-FL-A-RTF4-26L-40K-DB	400W PSMH	4000K	26,500	16-1/16" H x 17-3/4" W x 7-5/16" D
High-Output LED Floodlight	C-FL-A-RTF4-26L-50K-DB	400W PSMH	5000K	26,300	16-1/16" H x 17-3/4" W x 7-5/16" D
High-Output LED Floodlight	C-FL-A-RTS4-23L-40K-DB	400W PSMH	4000K	22,900	16-1/16" H x 17-3/4" W x 7-5/16" D
High-Output LED Floodlight	C-FL-A-RTS4-23L-50K-DB	400W PSMH	5000K	22,800	16-1/16" H x 17-3/4" W x 7-5/16" D
ACCESSORIES		SKU	SIZE/FITS		
LED Photocell 120V	C-ACC-A-PCCELL-LV	120V, Fits C-FL-A-RTF2, C-FL-A-RTS2, C-FL-A-RTF4, C-FL-A-RTS4 Series			
LED Photocell 208-277V	C-ACC-A-PCCELL-HV-TL	208-277V, Fits C-FL-A-RTF2, C-FL-A-RTS2, C-FL-A-RTF4, C-FL-A-RTS4 Series			

\*See lighting.cree.com/warranty for details



Architectural Wall Mount (120-277V)



LED Wall Mounts



LED Wall Mounts



LED High-Output Wall Mount



LED Wall Mounts

## LED WALL MOUNTS

Easy Installation; Versatile; Efficient

- Category: LED Outdoor Wall Mounts with Photo Cell
- CRI: >70
- Location Type: Wet
- Voltage: 120V
- Non-Dimmable
- High LPW: Up to 97
- Watts: 14 to 36

Item	SKU	Replaces	CCT	Lumens	Finish Color	Size/Fits
Architectural Wall Mount (120-277V)	C-WM-A-WLAR-11L-50K-MB	100W Incandescent	5000K	1,100	Medium Bronze	Size: 6" H x 5-2/5" W x 7-1/4" D
Wall Mount	C-WM-A-WLCY-6L-40K-WH	60W Incandescent	4000K	600	White	Size: 6-1/2" D x 4-3/4" W x 9-1/3" H
Wall Mount	C-WM-A-WLCY-6L-40K-DB	60W Incandescent	4000K	600	Dark Bronze	Size: 6-1/2" D x 4-3/4" W x 9-1/3" H
Wall Mount	C-WM-A-WLHR-10L-40K-MB	100W Incandescent	4000K	1,000	Medium Bronze	Size: 9" H x 5-3/4" W x 4" D
Wall Mount	C-WM-A-WLHR-10L-40K-WH	100W Incandescent	4000K	1,000	White	Size: 9" H x 5-3/4" W x 4" D
Wall Mount	C-WM-A-WLHR-12L-40K-MB	120W Incandescent	4000K	1,200	Medium Bronze	Size: 9" H x 5-3/4" W x 4" D
Wall Mount	C-WM-A-WLHR-12L-40K-WH	120W Incandescent	4000K	1,200	White	Size: 9" H x 5-3/4" W x 4" D
High-Output Wall Mount	C-WM-A-WLHO-36L-50K-MB	100W PSMH	5000K	3,600	Medium Bronze	Size: 11" H x 7-1/8" W x 4-1/4" D
High-Output Wall Mount	C-WM-A-WLHO-34L-40K-MB	100W PSMH	4000K	3,400	Medium Bronze	Size: 11" H x 7-1/8" W x 4-1/4" D
Wall Mount	C-WM-A-WLSL-14L-50K-MB	120W Incandescent	5000K	1,400	Medium Bronze	Size: 12-3/5" H x 7-3/4" W x 4-3/5" D
Wall Mount	C-WM-A-WLSP-8L-40K-WH	75W Incandescent	4000K	800	White	Size: 9-4/5" H x 4-2/5" W x 5-4/5" L
Wall Mount	C-WM-A-WLSP-8L-40K-DB	75W Incandescent	4000K	800	Dark Bronze	Size: 9-4/5" H x 4-2/5" W x 5-4/5" L

\*See [lighting.cree.com/warranty](http://lighting.cree.com/warranty) for details



Architectural Slim Wall Packs

## SLIMLINE LED WALL PACKS

**Efficient; Architectural Design; Easy Installation; 5 Year Limited Warranty\***

- Category: LED Outdoor Wall Packs
- CRI: >70
- Location Type: Wet
- Voltage: 120-277V
- Non-Dimmable
- Finish Color: Dark Bronze
- High LPW: Up to 105
- Watts: 40 to 150
- Cree LEDs, quality driver

Item	SKU	Replaces	CCT	Lumens	Watts	Size/Fits
Architectural Slim	C-WP-A-SL-4L-50K-DB	100W PSMH	5000K	3,900	40	Size: 8" H x 7-1/2" W x 2-4/5" D
Architectural Slim	C-WP-A-SL-4L-40K-DB	100W PSMH	4000K	3,900	40	Size: 8" H x 7-1/2" W x 2-4/5" D
Architectural Slim	C-WP-A-SL-8L-50K-DB	250W MH	5000K	8,100	80	Size: 12-4/5" H x 14-1/5" W x 5" D
Architectural Slim	C-WP-A-SL-8L-40K-DB	250W MH	4000K	8,100	80	Size: 12-4/5" H x 14-1/5" W x 5" D
Architectural Slim	C-WP-A-SL-16L-50K-DB	400W MH	5000K	15,800	150	Size: 12-4/5" H x 14-1/5" W x 5" D
Architectural Slim	C-WP-A-SL-16L-40K-DB	400W MH	4000K	15,800	150	Size: 12-4/5" H x 14-1/5" W x 5" D

**NOTE:** For Slimline LED Wall Pack Light accessories refer to Page 12; for General LED Wall Pack lighting accessories refer to page 14

\*See [lighting.cree.com/warranty](http://lighting.cree.com/warranty) for details



LED Photocell, 120V <1000W



Adjustable U-Bracket Mount Kit



Adjustable Slip Fitter



Adjustable Swivel Fitter



Adjustable U-Bracket



Surface Mounting Box

## SLIMLINE LED WALL PACK ACCESSORIES

Efficient; Architectural Design; Easy Installation; 5 Year Limited Warranty\*

- Category: LED Outdoor Accessories

Item	SKU	Size/Fits
LED Photocell, 120V	C-ACC-A-PCCELL-LV	120V, Fits C-WP-A Series
LED Photocell, 208-277V	C-ACC-A-PCCELL-HV	208-277V, Fits C-WP-A -SL Series
Adjustable U-Bracket	C-ACC-A-AUBAS-SM-DB	For Slimline Wallpacks C-WP-A-SL-4L Series
Adjustable Slip Fitter	C-ACC-A-2SFAS-SM-DB	2", For Slimline Wallpacks C-WP-A-SL-4L Series
Adjustable Swivel Fitter	C-ACC-A-12SFAS-SM-DB	1/2" NPS, For Slimline Wallpacks C-WP-A-SL-4L Series
Adjustable U-Bracket	C-ACC-A-AUBAS-LG-DB	For Slimline Wallpacks C-WP-A-SL-8L/16L Series
Adjustable Slip Fitter	C-ACC-A-2SFAS-LG-DB	2", For Slimline Wallpacks C-WP-A-SL-8L/16L Series
Surface Mounting Box	C-ACC-A-SMBAS-DB	For Slimline Wallpacks C-WP-A-SL-4L, C-WP-A-SL-8L/16L Series

\*See [lighting.cree.com/warranty](http://lighting.cree.com/warranty) for details



LED Wall Pack Traditional (non cutoff)

## LED WALL PACKS (NON CUTOFF)

Efficient; Easy Installation; 5 Year Limited Warranty\*

- Category: LED Outdoor Wall Packs
- CR1: >70
- Location Type: Wet
- Voltage: 120-277V
- Non-Dimmable
- Finish Color: Dark Bronze
- High LPW: Up to 144
- Watts: 20 to 158

Item	SKU	Replaces	CCT	Lumens	Watts	Size/Fits
Traditional (non cutoff) 120V only	C-WP-A-TR-1L-40K-DB	50W MH	4000K	1,300	20	Size: 8-9/16" H x 7-3/16" W x 7-5/16" L
Traditional (non cutoff)	C-WP-A-TRAD-3L- 40K-DB	100W PSMH	4000K	3,200	33	Size: 9-1/4" H x 14-1/8" W x 7-1/2" D
Traditional (non cutoff)	C-WP-A-TRAD-3L- 50K-DB	100W PSMH	5000K	3,400	33	Size: 9-1/4" H x 14-1/8" W x 7-1/2" D
Traditional (non cutoff)	C-WP-A-TR-4L-30K-DB	100W PSMH	3000K	4,600	43	Size: 9-1/4" H x 14-1/8" W x 7-1/2" D
Traditional (non cutoff)	C-WP-A-TR-4L-40K-DB	100W PSMH	4000K	4,600	43	Size: 9-1/4" H x 14-1/8" W x 7-1/2" D
Traditional (non cutoff)	C-WP-A-TR-4L-50K-DB	100W PSMH	5000K	4,600	43	Size: 9-1/4" H x 14-1/8" W x 7-1/2" D
Traditional (non cutoff)	C-WP-A-TRAD-8L- 40K-DB	250W MH	4000K	8,600	85	Size: 9-3/4" H x 18" W x 9-3/8" D
Traditional (non cutoff)	C-WP-A-TRAD-8L- 50K-DB	250W MH	5000K	8,900	87	Size: 9-3/4" H x 18" W x 9-3/8" D
Traditional (non cutoff)	C-WP-A-TR-12L-40K-DB	250W MH	4000K	13,000	108	Size: 9-5/6" H x 18" W x 9-3/8" D
Traditional (non cutoff)	C-WP-A-TR-12L-50K-DB	250W MH	5000K	13,100	108	Size: 9-5/6" H x 18" W x 9-3/8" D
Traditional (non cutoff)	C-WP-A-TR-15L-40K-DB	320W PSMH / 400W MH	4000K	15,000	119	Size: 9-7/8" H x 18" W x 13" D
Traditional (non cutoff)	C-WP-A-TR-15L-50K-DB	320W PSMH / 400W MH	5000K	15,300	119	Size: 9-7/8" H x 18" W x 13" D
Traditional (non cutoff)	C-WP-A-TR-21L-40K-DB	400W PSMH	4000K	21,100	158	Size: 9-3/4" H x 18" W x 9-3/8" D
Traditional (non cutoff)	C-WP-A-TR-21L-50K-DB	400W PSMH	5000K	21,100	158	Size: 9-3/4" H x 18" W x 9-3/8" D

NOTE: For General LED Wall Pack lighting accessories refer to page 14

\*See lighting.cree.com/warranty for details



LED Wall Pack Traditional (full cutoff) TRFC Series



LED Wall Pack Premium (full cutoff) FCT3 Series

## LED WALL PACKS (FULL CUTOFF)

Efficient; Easy Installation; 5 Year Limited Warranty\*

- Category: LED Outdoor Wall Packs
- CRI: >70
- Location Type: Wet
- Voltage: 120-277V
- Non-Dimmable
- Finish Color: Dark Bronze
- High LPW: Up to 144
- Watts: 20 to 157

Item	SKU	Replaces	CCT	Lumens	Watts	Size/Fits
Traditional (full cutoff)	C-WP-A-TRFC-6L-40K-DB	150W PSMH / 175W MH	4000K	6,400	66	Size: 14-1/4" D x 9-1/4" W x 9" H
Traditional (full cutoff)	C-WP-A-TRFC-6L-50K-DB	150W PSMH / 175W MH	5000K	6,600	66	Size: 14-1/4" D x 9-1/4" W x 9" H
Premium (full cutoff)	C-WP-A-FCT3-3L-30K-DB	100W PSMH	3000K	3,200	32	Size: 4-1/2" H x 8-3/4" W x 9-1/2" D
Premium (full cutoff)	C-WP-A-FCT3-3L-40K-DB	100W PSMH	4000K	3,500	33	Size: 4-1/2" H x 8-3/4" W x 9-1/2" D
Premium (full cutoff)	C-WP-A-FCT3-3L-50K-DB	100W PSMH	5000K	3,600	33	Size: 4-1/2" H x 8-3/4" W x 9-1/2" D
Premium (full cutoff)	C-WP-A-FCT3-6L-30K-DB	150W PSMH / 175W MH	3000K	5,100	57	Size: 4-11/16" H x 10" W x 10-5/16" D
Premium (full cutoff)	C-WP-A-FCT3-6L-40K-DB	150W PSMH / 175W MH	4000K	6,000	65	Size: 4-11/16" H x 10" W x 10-5/16" D
Premium (full cutoff)	C-WP-A-FCT3-6L-50K-DB	150W PSMH / 175W MH	5000K	6,200	66	Size: 4-11/16" H x 10" W x 10-5/16" D
Premium (full cutoff)	C-WP-A-FCT3-18L-40K-DB	320W PSMH / 400W MH	4000K	18,000	157	Size: 5-1/2" H x 13-1/2" W x 12-1/2" D
Premium (full cutoff)	C-WP-A-FCT3-18L-50K-DB	320W PSMH / 400W MH	5000K	18,000	157	Size: 5-1/2" H x 13-1/2" W x 12-1/2" D



LED Photocell, 120V <1000W

## LED WALL PACK ACCESSORIES

Efficient; Easy Installation; 5 Year Limited Warranty\*

- Category: LED Outdoor Accessories

Item	SKU	Size/Fits
LED Photocell, 120V	C-ACC-A-PCCELL-LV	120V, Fits C-WP-A Series
LED Photocell, 208-277V	C-ACC-A-PCCELL-HV	208-277V, Fits C-WP-A-TRAD/TRFC/TR Series
LED Photocell, 208-277V	C-ACC-A-PCCELL-HV-TL	208-277V, Fits C-WP-A FCT3 Series

\*See lighting.cree.com/warranty for details



LED Vapor Tight Pendant Mounts



LED Vapor Tight Wall Mounts



LED Vapor Tight Ceiling Mounts



LED Linear Vapor Tight Strip

## LED VAPOR TIGHTS

Efficient; Traditional Design; Easy To Install; 5 Year Limited Warranty\*

- Category: LED Outdoor Vapor Tights
- CRI: >70
- Location Type: Wet
- Voltage: 120V
- Non-Dimmable
- High LPW: Up to 98
- Watts: 14 to 22
- Cree LEDs, quality driver

Item	SKU	Replaces	CCT	Lumens	Finish Color	Size/Fits
LED Vapor Tight, Small Ceiling Mount	C-VT-A-SMCL-9L-40K-GR	100W Incandescent	4000K	900	Gray	9-1/3" H x 4-1/2" Diameter
LED Vapor Tight, Small Pendant Mount	C-VT-A-SMPD-9L-40K-GR	100W Incandescent	4000K	900	Gray	10" H x 4-1/2" Diameter
LED Vapor Tight, Small Wall Mount	C-VT-A-SMWL-9L-40K-GR	100W Incandescent	4000K	900	Gray	10" H x 4-2/5" W x 5-4/5" L
LED Vapor Tight, Large Ceiling Mount	C-VT-A-LGCL-12L-40K-GR	120W Incandescent	4000K	1,200	Gray	11-3/5" H x 5-4/5" Diameter
LED Vapor Tight, Large Pendant Mount	C-VT-A-LGPD-12L-40K-GR	120W Incandescent	4000K	1,200	Gray	12-2/5" H x 5-4/5" Diameter
LED Vapor Tight, Large Wall Mount	C-VT-A-LGWL-12L-40K-GR	120W Incandescent	4000K	1,200	Gray	Large - Wall Mount 12-2/5" H x 5-4/5" W x 9" L
LED Linear Vapor Tight Strip	C-VT-A-LIN4-52L-40K-GR	2-Lamp F32T8	4000K	5,200	Gray	50" L x 4-1/2" W x 3-1/2" H
LED Linear Vapor Tight Strip	C-VT-A-LIN4-52L-50K-GR	2-Lamp F32T8	5000K	5,200	Gray	50" L x 4-1/2" W x 3-1/2" H



LED Vapor Tight Shroud

## LED VAPOR TIGHT ACCESSORIES

Accessories for C-Lite™ LED Vapor Tights

Item	SKU	Finish Color	Size/Fits
LED Vapor Tight, Small Shroud	C-ACC-A-VTSHR-SM-GR	Gray	Small, For C-VT-A-SMCL/SMPD Series
LED Vapor Tight, Large Shroud	C-ACC-A-VTSHR-LG-GR	Gray	Large, For C-VT-A-LGCL/LGPD Series

\*See [lighting.cree.com/warranty](http://lighting.cree.com/warranty) for details



4" Downlight



6" Downlight



LED GU24 Connector

## LED DOWNLIGHTS

Best Combination of Performance and Value; 5 Year Limited Warranty\*

- Category: LED Downlights
- CRI: 90
- Location Type: Damp
- Voltage: 120V
- Input Power: 7.6 to 8.6 Watts
- Initial Delivered Lumens: 575 to 650
- Dimmable to 10%
- Base: E26

Item	SKU	Replaces	CCT	Lumens	Watts	Size/Fits
LED Downlight 4"	C-DL4-A-575L-27K-B1	55W Incandescent	2700K	575	7.6	2-9/10" H x 5" Dia (Trim Width)
LED Downlight 4"	C-DL4-A-575L-30K-B1	55W Incandescent	3000K	575	7.6	2-9/10" H x 5" Dia (Trim Width)
LED Downlight 4"	C-DL4-A-575L-40K-B1	55W Incandescent	4000K	575	7.6	2-9/10" H x 5" Dia (Trim Width)
LED Downlight 6"	C-DL6-A-650L-27K-B1	65W Incandescent	2700K	650	8.6	2-9/10" H x 7.2" Dia. (Trim Width)
LED Downlight 6"	C-DL6-A-650L-30K-B1	65W Incandescent	3000K	650	8.6	2-9/10" H x 7.2" Dia. (Trim Width)
LED Downlight 6"	C-DL6-A-650L-40K-B1	65W Incandescent	4000K	650	8.6	2-9/10" H x 7.2" Dia. (Trim Width)

ACCESSORIES	SKU	FITS
LED GU24 Connector	C-ACC-A-DL-GU24	120V, Fits C-DL4 & DL6 Series

\*See [lighting.cree.com/warranty](http://lighting.cree.com/warranty) for details



## LED DOWNLIGHTS

### High Efficacy and High Quality; 5 Year Limited Warranty\*

- Category: LED Downlights
- CRI: 90+
- Location Type: Damp and Wet
- Voltage: 120V
- Dimmable to 5%
- White, Metal Finish
- Mounting: Recessed



4" Downlight (E26)



6" Downlight (E26)



4" Downlight (GU24)



6" Downlight (GU24)

Both the E26 and GU24 Connector come standard with each downlight.

Item	SKU	Replaces	CCT	Lumens	Watts	Size/Fits
LED Downlight 4"	CR4T-790L-27K-12-E26GU24	75W Incandescent	2700K	790	10.5	2.6" H x 5" Dia (Trim Width)
LED Downlight 4"	CR4T-790L-30K-12-E26GU24	75W Incandescent	3000K	790	10.5	2.6" H x 5" Dia (Trim Width)
LED Downlight 4"	CR4T-790L-35K-12-E26GU24	75W Incandescent	3500K	790	10.5	2.6" H x 5" Dia (Trim Width)
LED Downlight 4"	CR4T-790L-40K-12-E26GU24	75W Incandescent	4000K	790	10.5	2.6" H x 5" Dia (Trim Width)
LED Downlight 6"	CR6T-825L-27K-12-E26GU24	75W Incandescent	2700K	825	11	3.5" H x 7.4" Dia (Trim Width)
LED Downlight 6"	CR6T-825L-30K-12-E26GU24	75W Incandescent	3000K	825	11	3.5" H x 7.4" Dia (Trim Width)
LED Downlight 6"	CR6T-825L-35K-12-E26GU24	75W Incandescent	3500K	825	11	3.5" H x 7.4" Dia (Trim Width)
LED Downlight 6"	CR6T-825L-40K-12-E26GU24	75W Incandescent	4000K	825	11	3.5" H x 7.4" Dia (Trim Width)
LED Downlight 6"	CR6T-1100L-27K-12-E26GU24	100W Incandescent	2700K	1,100	14.5	3.5" H x 7.4" Dia (Trim Width)
LED Downlight 6"	CR6T-1100L-30K-12-E26GU24	100W Incandescent	3000K	1,100	14.5	3.5" H x 7.4" Dia (Trim Width)
LED Downlight 6"	CR6T-1100L-35K-12-E26GU24	100W Incandescent	3500K	1,100	14.5	3.5" H x 7.4" Dia (Trim Width)
LED Downlight 6"	CR6T-1100L-40K-12-E26GU24	100W Incandescent	4000K	1,100	14.5	3.5" H x 7.4" Dia (Trim Width)
LED Downlight 6"	CR6T-1600L-27K-12-E26GU24	150W Incandescent	2700K	1,600	21	3.5" H x 7.4" Dia (Trim Width)
LED Downlight 6"	CR6T-1600L-30K-12-E26GU24	150W Incandescent	3000K	1,600	21	3.5" H x 7.4" Dia (Trim Width)
LED Downlight 6"	CR6T-1600L-35K-12-E26GU24	150W Incandescent	3500K	1,600	21	3.5" H x 7.4" Dia (Trim Width)
LED Downlight 6"	CR6T-1600L-40K-12-E26GU24	150W Incandescent	4000K	1,600	21	3.5" H x 7.4" Dia (Trim Width)

NOTE: For Downlight accessories refer to Page 18

\*See [lighting.cree.com/warranty](http://lighting.cree.com/warranty) for details



Black Satin Nickel Bronze



CRT Downlight Trims

## LED DOWNLIGHT ACCESSORIES

### Accessories for Cree® CRT Downlights

ACCESSORIES	SKU	FITS
4" Downlight Plastic Trim - <b>Black</b>	CR4T-TRMBKAN-1	CR4T Series Downlights
4" Downlight Plastic Trim - <b>Satin Nickel</b>	CR4T-TRMSTAN-1	CR4T Series Downlights
4" Downlight Plastic Trim - <b>Bronze</b>	CR4T-TRMBRAN-1	CR4T Series Downlights
6" Downlight Plastic Trim - <b>Black</b>	CR6T-TRMBKAN-1	CR6T Series Downlights
6" Downlight Plastic Trim - <b>Satin Nickel</b>	CR6T-TRMSTAN-1	CR6T Series Downlights
6" Downlight Plastic Trim - <b>Bronze</b>	CR6T-TRMBRAN-1	CR6T Series Downlights
6" Downlight Plastic Trim - <b>Black</b> with Extended Black Flange	CR6T-TRMBKBB-1	CR6T Series Downlights

\*See [lighting.cree.com/warranty](http://lighting.cree.com/warranty) for details

## LED SURFACE MOUNT DISK LIGHTS

Maximum flexibility for installation; High Efficacy and High Quality; 5 Year Limited Warranty\*

- Category: LED Surface Mount Disk Light
- CRI: 90+
- Location Type: Damp and Wet
- Voltage: 120V
- Dimmable to 5% with select dimmers
- LPW: 83
- White, Metal Finish
- Mounting: Surface Mount



4" Surface Mount Disk Light



6" Surface Mount Disk Light

Item	SKU	Replaces	CCT	Lumens	Watts	Size/Fits
LED Surface Mount Disk Light 4"	DS4-750L-27K-U1	65W Incandescent	2700K	750	9	1.9" H x 6" Dia (Trim Width)
LED Surface Mount Disk Light 4"	DS4-750L-30K-U1	65W Incandescent	3000K	750	9	1.9" H x 6" Dia (Trim Width)
LED Surface Mount Disk Light 4"	DS4-750L-40K-U1	65W Incandescent	4000K	750	9	1.9" H x 6" Dia (Trim Width)
LED Surface Mount Disk Light 6"	DS6-900L-27K-U1	75W Incandescent	2700K	900	10.5	2.3" H x 7.4" Dia (Trim Width)
LED Surface Mount Disk Light 6"	DS6-900L-30K-U1	75W Incandescent	3000K	900	10.5	2.3" H x 7.4" Dia (Trim Width)
LED Surface Mount Disk Light 6"	DS6-900L-40K-U1	75W Incandescent	4000K	900	10.5	2.3" H x 7.4" Dia (Trim Width)

## LED SURFACE MOUNT DISK LIGHT ACCESSORIES

Downlight Adapter Accessory Packs for Cree® Surface Mount Disk Lights



4" Disk Light GU24 Accessory Kit

4" Disk Light E26 Accessory Kit



6" Disk Light GU24 Accessory Kit

6" Disk Light E26 Accessory Kit

ACCESSORIES	SKU	FITS
<b>4" Disk Light GU24 Accessory Kit</b> Includes GU24 socket adapter and flip clip mount for use in recessed cans with GU24 sockets	DS4-GU24-ACCES-1	LED Surface Mount Disk Light 4"
<b>4" Disk Light E26 Accessory Kit</b> Includes E26 socket adapter and flip clip mount for use in recessed cans with Edison sockets	DS4-E26-ACCES-1	LED Surface Mount Disk Light 4"
<b>6" Disk Light GU24 Accessory Kit</b> Includes GU24 socket adapter and flip clip mount for use in recessed cans with GU24 sockets	DS6-GU24-ACCES-1	LED Surface Mount Disk Light 6"
<b>6" Disk Light E26 Accessory Kit</b> Includes E26 socket adapter and flip clip mount for use in recessed cans with Edison sockets	DS6-E26-ACCES-1	LED Surface Mount Disk Light 6"

\*See lighting.cree.com/warranty for details



1' X 4' LED Flat Panel



2' X 2' LED Flat Panel



2' X 4' LED Flat Panel

## LED FLAT PANEL TROFFERS

**Low Profile Design; High Efficiency; 5 Year Limited Warranty\***

- Category: LED Indoor Troffers
- CRI: 80
- Location Type: Damp
- Voltage: 120-277V
- Non-Dimmable, 0-10V
- White
- Watts: 40 or 50
- Mounting: Recessed

Item	SKU	Replaces	CCT	Lumens	Watts	Size/Fits
LED Flat Panel Troffer 1' X 4'	C-TR-A-FP14-40L-35K-WH	2 x F32T8	3500K	4,000	40	47-3/4" L x 11-3/4" W x 1/2" H (Panel)
LED Flat Panel Troffer 1' X 4'	C-TR-B-FP14-40L-40K-WH	2 x F32T8	4000K	4,000	40	47-3/4" L x 11-3/4" W x 1/2" H (Panel)
LED Flat Panel Troffer 1' X 4'	C-TR-A-FP14-40L-50K-WH	2 x F32T8	5000K	4,000	40	47-3/4" L x 11-3/4" W x 1/2" H (Panel)
LED Flat Panel Troffer 2' X 2'	C-TR-A-FP22-40L-35K-WH	2 x F32T8/U6	3500K	4,000	40	23-3/4" L x 23-3/4" W x 1/2" H (Panel)
LED Flat Panel Troffer 2' X 2'	C-TR-A-FP22-40L-40K-WH	2 x F32T8/U6	4000K	4,000	40	23-3/4" L x 23-3/4" W x 1/2" H (Panel)
LED Flat Panel Troffer 2' X 2'	C-TR-A-FP22-40L-50K-WH	2 x F32T8/U6	5000K	4,000	40	23-3/4" L x 23-3/4" W x 1/2" H (Panel)
LED Flat Panel Troffer 2' X 4'	C-TR-A-FP24-50L-35K-WH	3 x F32T8	3500K	5,000	50	47-3/4" L x 23-3/4" W x 1/2" H (Panel)
LED Flat Panel Troffer 2' X 4'	C-TR-B-FP24-50L-40K-WH	3 x F32T8	4000K	5,000	50	47-3/4" L x 23-3/4" W x 1/2" H (Panel)
LED Flat Panel Troffer 2' X 4'	C-TR-B-FP24-50L-50K-WH	3 x F32T8	5000K	5,000	50	47-3/4" L x 23-3/4" W x 1/2" H (Panel)

**NOTE:** For General LED lighting accessories refer to page 25

\*See [lighting.cree.com/warranty](http://lighting.cree.com/warranty) for details

## LED STRIPS & WRAPS

Easy Installation; High Efficiency; 5 Year Limited Warranty\*

- Category: LED Strips & Wraps
- CRI: ≥80
- Location Type: Damp
- Voltage: 120-277V
- 0-10V Dimming
- Finish Color: White
- Watts: 19 or 39
- Mounting Height: 8 to 12 feet



2 Ft. LED Linear Wrap



4 Ft. LED Linear Wrap

Item	SKU	Replaces	CCT	Lumens	Watts	Size/Fits
LED Linear Wrap 2-ft.	C-WR-A-WLIN2-24L-30K-WH	70W MH	3000K	2,400	19	24 3/8" L x 5 1/8" W x 2 3/4" H
LED Linear Wrap 2-ft.	C-WR-A-WLIN2-24L-35K-WH	70W MH	3500K	2,400	19	24 3/8" L x 5 1/8" W x 2 3/4" H
LED Linear Wrap 2-ft.	C-WR-A-WLIN2-24L-40K-WH	70W MH	4000K	2,400	19	24 3/8" L x 5 1/8" W x 2 3/4" H
LED Linear Wrap 4-ft.	C-WR-A-WLIN4-48L-30K-WH	100PSMH	3000K	4,800	39	48" L x 5 1/8" W x 2 3/4" H
LED Linear Wrap 4-ft.	C-WR-A-WLIN4-48L-35K-WH	100PSMH	3500K	4,800	39	48" L x 5 1/8" W x 2 3/4" H
LED Linear Wrap 4-ft.	C-WR-A-WLIN4-48L-40K-WH	100PSMH	4000K	4,800	39	48" L x 5 1/8" W x 2 3/4" H

\*See [lighting.cree.com/warranty](http://lighting.cree.com/warranty) for details



LED Round Low Bay

## LED ROUND LOW BAYS

Easy Installation; High Efficiency; 5 Year Limited Warranty\*

- Category: LED Indoor High Bays and Low Bays
- CRI: >70
- Location Type: Damp
- Voltage: 120-277V
- Non-Dimmable
- Finish Color: White
- High LPW: Up to 124
- Watts: 59
- Cree LEDs, quality driver

Item	SKU	Replaces	CCT	Lumens	Watts	Size/Fits
LED Round Low Bay	C-LB-A-RDAL-8L-50K-WH	150W PSMH 175W MH	5000K	8,000	59	10" H x 14" W x 6-1/2" L
LED Round Low Bay	C-LB-A-RDAL-8L-40K-WH	150W PSMH 175W MH	4000K	8,000	59	10" H x 14" W x 6-1/2" L
LED Round Low Bay	C-LB-A-RDAC-8L-50K-WH	150W PSMH 175W MH	5000K	8,000	59	10" H x 14" W x 6-1/2" L
LED Round Low Bay	C-LB-A-RDAC-8L-40K-WH	150W PSMH 175W MH	4000K	8,000	59	10" H x 14" W x 6-1/2" L

**NOTE:** For LED High & Low Bay Light Accessories refer to Page 24, for General LED lighting accessories refer to page 25

\*See [lighting.cree.com/warranty](http://lighting.cree.com/warranty) for details

## LED LINEAR HIGH BAYS

Easy Installation; High Efficiency; 5 Year Limited Warranty\*

- Category: LED Indoor Linear High Bays
- CRI: 80
- Location Type: Damp
- Voltage: 120-277V
- Non-Dimmable, 0-10V
- White
- High LPW: Up to 129
- Watts: 108 to 220



LED Linear High Bay



Premium LED Linear High Bay



Premium LED Linear High Bay

Item	SKU	Replaces	CCT	Lumens	Watts	Size/Fits
Linear High Bay	C-HB-A-L4F-20L-50K-WH	4-lamp T5HO 54W 8-lamp T8 32W	5000K	20,500	160	3-1/2" H x 12" W x 47-1/2" L
Linear High Bay	C-HB-A-L4F-28L-50K-WH	6-lamp T5HO 54W	5000K	28,500	220	3-1/2" H x 12" W x 47-1/2" L
Premium Linear High Bay	C-PHB-A-L2F-13L-40K-WH	6-lamp T8 32W	4000K	13,000	108	3-3/5" H x 12-3/5" W x 23-4/5" L
Premium Linear High Bay	C-PHB-A-L2F-13L-50K-WH	6-lamp T8 32W	5000K	13,000	108	3-3/5" H x 12-3/5" W x 23-4/5" L
Premium Linear High Bay	C-PHB-A-L2F-20L-40K-WH	4-lamp T5HO 54W 8-lamp T8 32W	4000K	20,000	160	3-3/5" H x 17-3/10" W x 23-4/5" L
Premium Linear High Bay	C-PHB-A-L2F-20L-50K-WH	4-lamp T5HO 54W 8-lamp T8 32W	5000K	20,000	160	3-3/5" H x 17-3/10" W x 23-4/5" L
Premium Linear High Bay	C-PHB-A-L4F-27L-40K-WH	6-lamp T5HO 54W	4000K	27,000	220	3-3/5" H x 12-3/5" W x 46" L
Premium Linear High Bay	C-PHB-A-L4F-27L-50K-WH	6-lamp T5HO 54W	5000K	27,000	220	3-3/5" H x 12-3/5" W x 46" L

**NOTE:** For LED High & Low Bay Light Accessories refer to Page 24, for General LED lighting accessories refer to page 25

\*See [lighting.cree.com/warranty](http://lighting.cree.com/warranty) for details




Premium Linear High Bay PIR Sensor



Premium Linear High Bay Pendant Mount Kit



Linear High Bay Frosted Lens



Premium Linear High Bay Wire Guard



LED Hook & Cord Kits



1/2" Hook

## LED HIGH & LOW BAY ACCESSORIES

### Accessories for C-Lite™ LED High & Low Bays

Item	SKU	Size/Fits
Premium Linear High Bay PIR Sensor	C-PHB-A-HBPIR	Suits C-PHB Series
Premium Linear High Bay Pendant Mount Kit	C-PHB-A-HBPM	Suits C-PHB Series
Linear High Bay Frosted Lens	C-HB-A-LHBFL-12X48	Suits C-HB Series 12" x 47-1/2" Fixtures
Premium Linear High Bay Wire Guard	C-PHB-A-LHBWG-12X24	Suits C-PHB Series 12-3/5" x 23-4/5" Fixtures
Premium Linear High Bay Wire Guard	C-PHB-A-LHBWG-18X24	Suits C-PHB Series 17-3/10" x 23-4/5" Fixtures
Premium Linear High Bay Wire Guard	C-PHB-A-LHBWG-12X46	Suits C-PHB Series 12-3/5" x 46" Fixtures
LED Hook & Cord Kit, 6 ft, 120-277V, No Plug	C-ACC-A-HKCRD-6FT-LV-NP	6ft, 120V-277V, No Plug, Fits 120-277V High Bays / Low Bays
LED Hook & Cord Kit, 6 ft, 120V, Twist Lock Plug	C-ACC-A-HKCRD-6FT-LV-TL	6ft, 120V, Twist Lock Plug, Fits 120V High Bays / Low Bays
LED Hook & Cord Kit, 6 ft, 120V, Straight Blade Plug	C-ACC-A-HKCRD-6FT-LV-SB	6ft, 120V, Straight Blade Plug, Fits 120V High Bays / Low Bays
LED Hook & Cord Kit, 6 ft, 277V, Twist Lock Plug	C-ACC-A-HKCRD-6FT-HV-TL	6ft, 277V, Twist Lock Plug, Fits 277V High Bays / Low Bays
LED Hook & Cord, 208-240V, Twist Lock Plug	C-ACC-A-HKCRD-6FT-MV-TL	6ft, 208-240V, Twist Lock Plug, Fits 208-240V High Bays / Low Bays
1/2" Hook	C-ACC-A-HK12	1/2", Fits High Bays / Low Bays

\*See [lighting.cree.com/warranty](http://lighting.cree.com/warranty) for details





Cord, 6 ft. Straight Blade Plug



Cord, 6 ft, Twist Lock Plug



Receptacle, 15A, Twist Lock

## GENERAL LED ACCESSORIES

### Quality; Reliability

- Voltage: 120-277V

Item	SKU	Size/Fits
LED Cord w-Strain Relief	C-ACC-A-CRDS-6FT-LV-TL	6ft, 120V, Twist Lock Plug, Fits any 120V Fixture
LED Cord w-Strain Relief	C-ACC-A-CRDS-6FT-LV-SB	6ft, 120V, Straight Blade Plug, Fits any 120V Fixture
LED Cord w-Strain Relief	C-ACC-A-CRDS-6FT-HV-TL	6ft, 277V, Twist Lock Plug, Fits any 277V Fixture
LED Cord w-Strain Relief	C-ACC-A-CRDS-6FT-MV-TL	6ft, 208-240V, Twist Lock Plug, Fits any 208-240V Fixture
LED Cord	C-ACC-A-CRD-6FT-LV-TL	6ft, 120V, Twist Lock Plug, Fits any 120V Fixture
LED Cord	C-ACC-A-CRD-6FT-LV-SB	6ft, 120V, Straight Blade Plug, Fits any 120V Fixture
LED Cord	C-ACC-A-CRD-6FT-MV-TL	6ft, 208-240V, Twist Lock Plug, Fits any 208-240V Fixture
LED Cord	C-ACC-A-CRD-6FT-HV-TL	6ft, 277V, Twist Lock Plug, Fits any 277V Fixture
LED Receptacle	C-ACC-A-RECEP-LV-TL	3-Wire, 15A / 120V, Twist Lock
LED Receptacle	C-ACC-A-RECEP-HV-TL	3-Wire, 15A / 277V, Twist Lock
LED Receptacle	C-ACC-A-RECEP-MV-TL	3-Wire, 15A / 208-240V, Twist Lock

\*See [lighting.cree.com/warranty](http://lighting.cree.com/warranty) for details



A19



BR30

## LED LAMPS

**Best Combination of Performance and Value; 5 Year Limited Warranty\***

- Category: LED Lamps
- CRl: ≥ 80
- Initial Delivered Lumens: 440 to 1,050
- Dimmable: Yes (-DIM Series)
- Base: E26

Item	SKU	Replaces	CCT	Lumens	Watts	LPW	Base Type	Pack Size
LED A19 Lamp	C-A19-A-40W-ND-27K-B4	40W Incandescent	2700K	440	5.5	80	E26	4 Pack
LED A19 Lamp	C-A19-A-60W-ND-27K-B4	60W Incandescent	2700K	750	9.0	84	E26	4 Pack
LED A19 Lamp	C-A19-A-60W-ND-30K-B4	60W Incandescent	3000K	750	9.0	84	E26	4 Pack
LED A19 Lamp	C-A19-A-75W-ND-27K-B2	75W Incandescent	2700K	1,050	11.0	95	E26	2 Pack
LED A19 Energy Star Lamp	C-A19-A-40W-DIM-27K-B2	40W Incandescent	2700K	450	6.0	75	E26	2 Pack
LED A19 Energy Star Lamp	C-A19-A-60W-DIM-27K-B2	60W Incandescent	2700K	800	9.0	89	E26	2 Pack
LED A19 Energy Star Lamp	C-A19-A-60W-DIM-30K-B2	60W Incandescent	3000K	800	9.0	89	E26	2 Pack
LED A19 Energy Star Lamp	C-A19-A-75W-DIM-27K-B2	75W Incandescent	2700K	1,100	12.0	92	E26	2 Pack
LED BR30 Lamp	C-BR30-A-65W-DIM-27K-B2	65W Incandescent	2700K	750	8.5	88	E26	2 Pack
LED BR30 Lamp	C-BR30-A-65W-DIM-30K-B2	65W Incandescent	3000K	800	8.5	94	E26	2 Pack

\*See [lighting.cree.com/warranty](http://lighting.cree.com/warranty) for details



A19



A21

## CREE® PROFESSIONAL SERIES A19 & A21 LED LAMPS

PRO  
SERIES

Light your space like a Pro; 5 Year Limited Warranty\*

- A19 Series & A21 Series
- CRI: 90+
- Omnidirectional Light
- Smooth Dimming
- Damp Location Rated
- Meets ENERGY STAR, CEC Title 20/Title 24 JA-8 requirements

Item	SKU	Replaces	CCT	Lumens	Watts	LPW	Base Type
Pro Series A19 LED Lamp	A19-40W-P1-27K-E26-U1	40W Incandescent	2700K	460	5.5	84	E26
Pro Series A19 LED Lamp	A19-40W-P1-30K-E26-U1	40W Incandescent	3000K	460	5.5	84	E26
Pro Series A19 LED Lamp	A19-40W-P1-50K-E26-U1	40W Incandescent	5000K	460	5.5	84	E26
Pro Series A19 LED Lamp	A19-60W-P1-27K-E26-U1	60W Incandescent	2700K	815	10	81	E26
Pro Series A19 LED Lamp	A19-60W-P1-30K-E26-U1	60W Incandescent	3000K	815	10	81	E26
Pro Series A19 LED Lamp	A19-60W-P1-40K-E26-U1	60W Incandescent	4000K	815	10	81	E26
Pro Series A19 LED Lamp	A19-60W-P1-50K-E26-U1	60W Incandescent	5000K	815	10	81	E26
Pro Series A19 LED Lamp	A19-75W-P1-27K-E26-U1	75W Incandescent	2700K	1,100	12	92	E26
Pro Series A19 LED Lamp	A19-75W-P1-30K-E26-U1	75W Incandescent	3000K	1,100	12	92	E26
Pro Series A19 LED Lamp	A19-75W-P1-50K-E26-U1	75W Incandescent	5000K	1,100	12	92	E26
Pro Series A21 LED Lamp	A21-100W-P1-27K-E26-U1	100W Incandescent	2700K	1,600	17	94	E26
Pro Series A21 LED Lamp	A21-100W-P1-30K-E26-U1	100W Incandescent	3000K	1,600	17	94	E26
Pro Series A21 LED Lamp	A21-100W-P1-50K-E26-U1	100W Incandescent	5000K	1,600	17	94	E26
Pro Series A21 3-Way LED Lamp	A21-3WAY-P1-27K-E26-U1	3 Way Incandescent	2700K	450/ 800/ 1,420	5.5/ 9/17	84	E26

PRO SERIES A - LED LAMPS

\*See [lighting.cree.com/warranty](http://lighting.cree.com/warranty) for details



PAR38

## CREE® PROFESSIONAL SERIES PAR38 LED LAMPS

Light your space like a Pro; 5 Year Limited Warranty\*

- PAR38 Series
- Focused 40° flood beam
- 90+ CRI
- Smooth Dimming
- Meets ENERGY STAR, CEC Title 20/Title 24 JA-8 requirements

Item	SKU	Replaces	CCT	Lumens	Watts	LPW	Base Type
Pro Series PAR38 LED Lamp	PAR38-150W-30K-40FL-E26-U1	150W Incandescent	3000K	1,500	19	79	E26

\*See [lighting.cree.com/warranty](http://lighting.cree.com/warranty) for details

CREE® PROFESSIONAL SERIES BR30, BR40 & R20 LED LAMPS

PRO SERIES

Optimal for recessed downlights and track lights; 5 Year Limited Warranty\*

- BR30, BR40 & R20 Series
- CRI: 90+
- Flood Lighting
- Smooth Dimming
- Damp Location Rated
- Meets ENERGY STAR, CEC Title 20/Title 24 JA-8 requirements

PRO SERIES REFLECTOR LED LAMPS



BR30



BR40



R20

Item	SKU	Replaces	CCT	Lumens	Watts	LPW	Base Type
Cree BR30 LED Lamp	BR30-65W-27K-U1	65W Incandescent	2700K	665	8.8	76	E26
Cree BR30 LED Lamp	BR30-65W-30K-U1	65W Incandescent	3000K	665	8.8	76	E26
Cree BR30 LED Lamp	BR30-65W-40K-U1	65W Incandescent	4000K	665	8.8	76	E26
Pro Series BR30 LED Lamp	BR30-100W-P1-27K-E26-U1	100W Incandescent	2700K	1,400	16	87	E26
Pro Series BR30 LED Lamp	BR30-100W-P1-30K-E26-U1	100W Incandescent	3000K	1,400	16	87	E26
Pro Series BR30 LED Lamp	BR30-100W-P1-50K-E26-U1	100W Incandescent	5000K	1,400	16	87	E26
Pro Series BR40 LED Lamp	BR40-120W-P1-27K-E26-U1	120W Incandescent	2700K	1,750	23	76	E26
Pro Series BR40 LED Lamp	BR40-120W-P1-30K-E26-U1	120W Incandescent	3000K	1,750	23	76	E26
Pro Series BR40 LED Lamp	BR40-120W-P1-50K-E26-U1	120W Incandescent	5000K	1,750	23	76	E26
Pro Series R20 LED Lamp	R20-50W-P1-27K-E26-U1	50W Incandescent	2700K	560	7	80	E26
Pro Series R20 LED Lamp	R20-50W-P1-50K-E26-U1	50W Incandescent	5000K	560	7	80	E26
Pro Series R20 LED Lamp	R20-75W-P1-27K-E26-U1	75W Incandescent	2700K	980	13	75	E26
Pro Series R20 LED Lamp	R20-75W-P1-50K-E26-U1	75W Incandescent	5000K	980	13	75	E26

\*See [lighting.cree.com/warranty](http://lighting.cree.com/warranty) for details



B11

## CREE® PROFESSIONAL SERIES B11 LED LAMPS

PRO  
SERIES

Optimal for decorative lighting, chandeliers, and ceiling fans; 5 Year Limited Warranty\*

- Category: LED Lamps
- B11 Series
- Clear glass shell offers omnidirectional light
- 90+ CRI
- Smooth Dimming
- Meets ENERGY STAR, CEC Title 20/Title 24 JA-8 requirements

Item	SKU	Replaces	CCT	Lumens	Watts	LPW	Base Type
Pro Series B11 LED Lamp	B11-25W-P1-27K-E12-U1	25W Incandescent	2700K	220	2.6	85	E12
Pro Series B11 LED Lamp	B11-25W-P1-50K-E12-U1	25W Incandescent	5000K	220	2.6	85	E12
Pro Series B11 LED Lamp	B11-40W-P1-27K-E12-U1	40W & 60W Incandescent	2700K	350	4	87	E12
Pro Series B11 LED Lamp	B11-40W-P1-50K-E12-U1	40W & 60W Incandescent	5000K	350	4	87	E12
Pro Series B11 LED Lamp	B11-60W-P1-27K-E12-U1	40W & 60W Incandescent	2700K	515	5.5	94	E12
Pro Series B11 LED Lamp	B11-60W-P1-50K-E12-U1	40W & 60W Incandescent	5000K	515	5.5	94	E12

\*See [lighting.cree.com/warranty](http://lighting.cree.com/warranty) for details



Learn more at: [c-lite.com](http://c-lite.com) and [lighting.cree.com](http://lighting.cree.com) | 800.236.6800

---

PRO  
SERIES

**C-LITE**  
LED LIGHTING BY CREE

**CREE** 

©2018 Cree, Inc. All rights reserved. For informational purposes only. Not a warranty or specification. Cree® and the Cree logo are registered trademarks and C-Lite™ and the C-Lite logo are trademarks of Cree Inc. ENERGY STAR® is a registered trademark of U.S. EPA.  
CAT/CREE-0515 Rev. Date 10/25/2018