



# Landscape Lighting

Westgate is a leading manufacturer of Landscape Lights. Westgate offers a wide selection of modern and traditional options designed around the latest in outdoor LED technology. Indulge yourself! Integrate and optimize to your budget while enjoying the quality, style and features of each model.





### 12V INTEGRATED LED LANDSCAPE UPLIGHTS

:: Catalog No.	LFLV-7W-30K LFLV-7W-50K	LFLV-12W-30K LFLV-12W-50K
:: Wattage	7W	12W
:: Lumens	500 (30K), 550 (50K)	800 (30K), 900 (50K)
:: Voltage	12V AC/DC (Tolerance: 8-14V AC/DC 7W, 11-14V AC/DC 12W)	
:: Color Temp	3000K Warm White (30K), 5000K Cool White (50K)	
:: Beam Angle	40°	60°
:: Light Source	Nichia 757 UL-Recognized LED Controller and SMD LED Array (Non-Dimmable)	
:: Housing / Finish	ADC 12 Cast Aluminum with Powder Coat (Bronze Finish)	
:: Lens	Optical Polycarbonate Lens	Prismatic Reflector + Optic LED Lens and Glass Front Lens
:: Dimensions		
:: Accessories included	 Silicon-filled Wire Nuts  8-1/2" Non-metallic Spike  2ft. SPT-2 18AWG Lead Wire  Integrated SMD board and Optical Lens  WET location  IP67  1 YEAR WARRANTY	

C1

12V LED LANDSCAPE LIGHTS



12V INTEGRATED LED LANDSCAPE FLOOD LIGHTS

C2

12V LED LANDSCAPE LIGHTS

:: Catalog No.	FLV12-6W-30K FLV12-6W-50K	FLV12-12W-30K FLV12-12W-50K	FLV12-24W-30K FLV12-24W-50K	FLV12-32W-30K FLV12-32W-50K
:: Wattage	6W	12W	24W	32W
:: Lumens	600LM	1200LM	2400LM	3200LM
:: Voltage	12V AC/DC (Tolerance: 12-18V AC, 10-26V DC)			
:: Color Temp	3000K Warm White (30K), 5000K Cool White (50K)			
:: Beam Angle	60°			
:: Light Source	Philips Lumileds (Non-dimmable)			
:: Housing / Finish	ADC 12 Cast Aluminum with Powder Coat (Bronze Finish)			
:: Lens	Optical Polycarbonate Lens			
:: Dimensions				
:: Accessories included	Silicon-filled Wire Nuts                  Non-metallic Spike                  3ft. SPT-2 18AWG Lead Wire (6W 22AWG)                  PHILIPS LUMILEDS                  WET location IP67                  7 YEAR LIMITED WARRANTY			



### 12V INTEGRATED LED WALL WASH LIGHTS

:: Catalog No.	LF4-12V-6W-30K LF4-12V-6W-50K	LF4-12V-12W-30K LF4-12V-12W-50K	LF4-12V-24W-30K LF4-12V-24W-50K	LF4-12V-30W-30K LF4-12V-30W-50K	LF4-12V-50W-30K LF4-12V-50W-50K
:: Wattage	6W	12W	24W	30W	50W
:: Lumens	440 (30K), 500 (50K)	1080 (30K), 1260 (50K)	2155 (30K), 2500 (50K)	2700 (30K), 3150 (50K)	4500 (30K), 5250 (50K)
:: Voltage	12V AC/DC (Tolerance: 12-18V AC, 10-26V DC)				
:: Color Temp	3000K Warm White (30K), 5000K Cool White (50K)				
:: Beam Angle	120° X 90°				
:: Light Source	Philips Lumileds (Non-dimmable)				
:: Housing / Finish	ADC 12 Cast Aluminum with Powder Coat (Bronze Finish)				
:: Lens	Optical Polycarbonate Lens				
:: Dimensions					

:: Accessories included

For surface mounting use A-41-BR base see accessories page C35

Silicon-filled  
Wire Nuts

8-1/2"  
Non-metallic Spike






3ft.  
SPT-2 18AWG  
Lead Wire  
(6W 22AWG)



C4

12V LED LANDSCAPE LIGHTS

### 12V LED GARDEN LIGHTS

:: Catalog No.	LF12-6WW LF12-6NW LF12-6CW
:: Wattage	5W (New Higher Efficiency, Same Lumens as Previous 6W)
:: Lumens	400LM (3200K) / 450LM (4000K) / 450LM (5000K)
:: Voltage	12V AC/DC (Tolerance: ±3V AC/DC)
:: Color Temp	3200K Warm White (WW), 4000K Natural White (NW), 5000K Cool White (CW)
:: Beam Angle	45°
:: Light Source	COB Technology with Smooth Aluminum Reflector (Non-dimmable)
:: Housing / Finish	ADC 12 Cast Aluminum with Powder Coat (Bronze Finish)
:: Lens	Glass Lens
:: Dimensions	
:: Accessories included	<div style="display: flex; justify-content: space-around; align-items: flex-start;"> <div style="text-align: center;">  <p>6-1/2" Aluminum Spike</p> </div> <div style="text-align: center;">  <p>18" SJO 18/2AWG Lead Wire</p> </div> <div style="text-align: center;">  <p>COB TECHNOLOGY</p> </div> <div style="text-align: center;">  <p>WET location IP67</p> </div> <div style="text-align: center;">  <p>1 YEAR WARRANTY</p> </div> </div>



12V LED DIRECTIONAL LIGHT - SOLID BRASS

:: Catalog No.	LFLD-5W-30K-BZ	LD-180-BZ
:: Housing / Finish	Solid Brass Antique Bronze Finish	
:: Wattage	5W	3W
:: Lumens	400LM	300LM
:: Voltage	12V AC/DC	12V AC/DC
:: Color Temp	3000K Warm White	3000K Warm White
:: Beam Angle	90° to 10° Adjustable with Telescopic Hood	80°
:: Light Source	CREE COB Technology (Non-Dimmable)	LED JC G4 Corn Lamp Bi-pin
:: Lens	Magnifying Glass Lens Adjusts Beam Angle from 90° to 10°	3 Different Lenses included: Clear, Frosted & Line Diffuser
:: Dimensions		
:: Accessories included		



C6

12V LED LANDSCAPE LIGHTS

**12VLED DIRECTIONAL LIGHTS- SOLID COPPER & SOLID BRASS**

:: Catalog No.	LD-098-CR	LD-176-CR	LD-176-BZ	LD-009-BZ
:: Housing / Finish	Cast Solid Copper, Natural Finish		Cast Solid Brass, Antique Bronze Finish	
:: Wattage	5W (Included), 7W LED Max.			
:: Lumens	400LM			
:: Voltage	12V AC/DC			
:: Color Temp	3000K Warm White			
:: Beam Angle	36°			
:: Light Source	5W LED Glass MR16 Lamp Included (WESTGATE Part Number: MR16-400L-30K-D)			
:: Lens	Convex Glass Lens			
:: Dimensions				
:: Accessories included				





**12V LED DIRECTIONAL LIGHTS - SOLID BRASS**

:: Catalog No.	LD-006-BZ	LD-103-BZ	LD-099-BZ	LD-174-BZ
:: Housing / Finish	Cast Solid Brass, Antique Bronze Finish			Spun Solid Brass
:: Wattage	5W (Included), 7W LED Max.			
:: Lumens	400LM			
:: Voltage	12V AC/DC			
:: Color Temp	3000K Warm White			
:: Beam Angle	36°			
:: Light Source	5W LED Glass MR16 Lamp Included (WESTGATE Part Number: MR16-400L-30K-D)			
:: Lens	Convex Glass Lens			
:: Dimensions				
:: Accessories included	<p>Silicon-filled Wire Nuts      8-1/2" Non-metallic Spike      3ft. SPT-2 18AWG Lead Wire      LED MR16 Lamp</p>			



**12V LED DIRECTIONAL LIGHTS – SOLID BRASS, CAST ALUMINUM, FIBER GLASS**

C8

12V LED LANDSCAPE LIGHTS

:: Catalog No.	LD-192-BZ	AD-192-BK AD-192-BR	AD-192-FBK
:: Housing / Finish	Cast Brass Antique Bronze (BZ)	Die-cast Aluminum Black (BK), Bronze (BR)	Fiberglass (Black)
:: Wattage	5W (Included), 7W LED Max.		
:: Lumens	400LM		
:: Voltage	12V AC/DC		
:: Color Temp	3000K Warm White		
:: Beam Angle	36°		
:: Light Source	5W LED glass MR16 Lamp Included (WESTGATE Part Number: MR16-400L-30K-D)		
:: Lens	Convex Glass Lens		
:: Dimensions			
:: Accessories included			











**12V LED DIRECTIONAL LIGHTS - ALUMINUM**


:: Catalog No.	AD-102-BK AD-102-BR	AD-003-BK AD-003-BR	AD-130-BK AD-130-BR	AD-131-BK AD-131-BR
:: Housing / Finish	Aluminum Black (BK), Bronze (BR)			
:: Wattage	5W (Included), 7W LED Max.			
:: Lumens	400LM			
:: Voltage	12V AC/DC			
:: Color Temp	3000K Warm White			
:: Beam Angle	36°			
:: Light Source	5W LED Glass MR16 Lamp Included (WESTGATE Part Number: MR16-400L-30K-D)			
:: Lens	Flat Glass Lens (Except AD-102 Convex)			
:: Dimensions				
:: Accessories included	Silicon-filled Wire Nuts                  8-1/2" Non-metallic Spike                  3ft. SPT-2 18AWG Lead Wire                  LED MR16 Lamp                  WET location IP67                  1 YEAR WARRANTY			









**AGED NICKEL COLLECTION**

AGED NICKEL COLLECTION

:: Catalog No.	LD-103-AN	LA-112-AN	LA-117-AN	LA-116-AN	LA-111-AN
:: Housing / Finish	Cast Brass, Aged Nickel Finish (Long-lasting Alternative to Stainless Steel)				
:: Wattage	5W (Included), 7W LED Max.		3W		
:: Lumens	400LM		200LM		
:: Voltage	12V AC/DC		12V AC/DC		
:: Color Temp	3000K Warm White		3000K Warm White		
:: Beam Angle	36°		360°		
:: Light Source	5W LED Glass MR16 Lamp Included		Integrated SMD LED TowerHeavy		
:: Lens	Flat Glass Lens		Duty Clear Glass Lens		
:: Diameter of Shade	For dimensional drawing see page C7	5-1/2"	7-7/8"	6-3/4"	8"
:: Total Height		23"	23"	23"	23"
:: Accessories included	 Silicon-filled Wire Nuts  8-1/2" Non-metallic Spike  3ft. SPT-2 18AWG Lead Wire  LED MR16 Lamp (LD-103-AN)  LED Tower (Path lights)  WET location  WET & TRANSFORMERS IP67  3 YEAR WARRANTY				



12V LED PATH LIGHTS





:: Catalog No.	LAL-126-BR	LAL-126-BK
:: Housing / Finish	Die-cast Aluminum - Powder-coated Bronze (BR) or Black (BK)	
:: Wattage	3W	
:: Lumens	200LM	
:: Voltage	12V AC/DC	
:: Color Temp	3000K Warm White	
:: Beam Angle	360°	
:: Light Source	Integrated SMD LED	
:: Lens	Frosted PC Lens	
:: Total Height	23"	
:: Accessories included	 Silicon-filled Wire Nuts  10" Non-metallic Spike  3ft. SPT-2 18AWG Lead Wire  LED Module  WET Location IP67  1 YEAR WARRANTY	



**12V LED AREA LIGHTS - SOLID BRASS**

C12

LED AREA LIGHTS

	<b>12V LED AREA LIGHTS - SOLID BRASS</b>			
:: Catalog No.	LA-STEM-BZ	LA-112-BZ	LA-115-BZ	LA-117-BZ
:: Housing / Finish	Solid Brass - Antique Bronze Finish			
:: Wattage	3W			
:: Lumens	200LM			
:: Voltage	12V AC/DC			
:: Color Temp	3000K Warm White			
:: Beam Angle	360°			
:: Light Source	Integrated SMD LED Tower Heavy			
:: Lens	Duty Clear Glass Lens			
:: Diameter of Shade	—	5-1/2"	5-3/8"	7-7/8"
:: Total Height	23"	23"	23"	23"
:: Accessories included	<p>If ordering stem and shade separately, add "-C" to fixture model for shade                      Example: LA-112-BZ-C (Shade only) + LA-STEM-BZ</p> <div style="display: flex; justify-content: space-around; align-items: flex-start;"> <div style="text-align: center;">  <p>Silicon-filled Wire Nuts</p> </div> <div style="text-align: center;">  <p>8-1/2" Non-metallic Spike</p> </div> <div style="text-align: center;">  <p>3ft. SPT-2 18AWG Lead Wire</p> </div> <div style="text-align: center;">  <p>LED Tower</p> </div> </div> <div style="text-align: right; margin-top: 10px;">    </div>			



**12V LED AREA LIGHTS - SOLID BRASS**

:: Catalog No.	LA-116-BZ	LA-118-BZ	LA-111-BZ
:: Housing / Finish	Solid Brass - Antique Bronze Finish		
:: Wattage	3W		
:: Lumens	200LM		
:: Voltage	12V AC/DC		
:: Color Temp	3000K Warm White		
:: Beam Angle	360°		
:: Light Source	Integrated SMD LED Tower Heavy		
:: Lens	Duty Clear Glass Lens		
:: Diameter of Shade	6-3/4"	6-7/8"	8"
:: Total Height	23"	23"	23"
:: Accessories included	<p>If ordering stem and shade separately, add "-C" to fixture model for shade                      Example: LA-112-BZ-C (Shade only) + LA-STEM-BZ</p> <div style="display: flex; justify-content: space-around; align-items: flex-start;"> <div style="text-align: center;">  <p>Silicon-filled Wire Nuts</p> </div> <div style="text-align: center;">  <p>8-1/2" Non-metallic Spike</p> </div> <div style="text-align: center;">  <p>3ft. SPT-2 18 AWG Lead Wire</p> </div> <div style="text-align: center;">  <p>LED Tower</p> </div> </div> <div style="text-align: right; margin-top: 10px;">    </div>		



**12V LED AREA LIGHTS SOLID BRASS**

C14

LED AREA LIGHTS

:: Catalog No.	LA-008-BZ	LA-010-BZ	LA-002-BZ
:: Housing / Finish	Solid Brass - Antique Bronze Finish		
:: Wattage	3W		
:: Lumens	200LM		
:: Voltage	12V AC/DC		
:: Color Temp	3000K Warm White		
:: Beam Angle	360°		
:: Light Source	Integrated SMD LED Tower		
:: Lens	Heavy-Duty Clear Glass Lens		
:: Diameter of Shade	5-1/2"	8-1/2"	5-1/2"
:: Total Height	20"	23"	23-1/2"
:: Accessories included	Stems and shades of the items on this page are not interchangeable with each other or other models   Silicon-filled Wire Nuts  8-1/2" Non-metallic Spike  3ft. SPT-2 18AWG Lead Wire  LED Tower    		





12V LED PAGODA LIGHTS







:: Catalog No.	AA-145-BR AA-145-BK	AA-146-BR AA-146-BK	AA-148-BK
:: Housing / Finish	Die-cast Aluminum - Powder-Coated Bronze Finish (BR), Black (BK)		
:: Wattage	3W		
:: Lumens	200LM		
:: Voltage	12V AC/DC		
:: Color Temp	3000K Warm White		
:: Beam Angle	360°		
:: Light Source	Integrated SMD LED Tower		
:: Lens	Heavy-Duty Clear Glass Lens		
:: Diameter of Shade	6"	6"	8-3/4"
:: Height of Stem	4"	13"	11"
:: Total Height	9-1/2"	13"	14-3/4"
:: Accessories included	 Silicon-filled Wire Nuts  8-1/2" Non-metallic Spike  3ft. SPT-2 18AWG Lead Wire  LED Tower  WET location  IP67  3 YEAR WARRANTY		



C16

LED AREA LIGHTS

**12V LED AREA LIGHTS – SOLID COPPER**

:: Catalog No.	LA-STEM-CR	LA-111-CR	LA-117-CR	LA-116-CR
:: Housing / Finish	Solid Copper, Natural Finish			
:: Wattage	3W			
:: Lumens	200LM			
:: Voltage	12V AC/DC			
:: Color Temp	3000K Warm White			
:: Beam Angle	360°			
:: Light Source	Integrated SMD LED Tower			
:: Lens	Heavy-Duty Clear Glass Lens			
:: Diameter of Shade	—	8"	7-3/4"	6-3/4"
:: Total Height	23"	23"	23"	23"
:: Accessories included	<p>If ordering stem and shade separately, add "-C" to fixture model for shade                      Example: LA-111-CR-C (Shade only) + LA-STEM-CR</p> <div style="display: flex; justify-content: space-around; align-items: flex-start;"> <div style="text-align: center;">  <p>Silicon-filled Wire Nuts</p> </div> <div style="text-align: center;">  <p>8-1/2" Non-metallic Spike</p> </div> <div style="text-align: center;">  <p>3ft. SPT-2 18AWG Lead Wire</p> </div> <div style="text-align: center;">  <p>LED Tower</p> </div> <div style="text-align: center;">  <p>WET location IP67</p> </div> <div style="text-align: center;">  <p>3 YEAR WARRANTY</p> </div> </div>			




12V LED AREA LIGHTS – SOLID COPPER


:: Catalog No.	LA-010-CR	LA-118-CR	LA-112-CR
:: Housing / Finish	Solid Copper, Natural Finish		
:: Wattage	3W		
:: Lumens	200LM		
:: Voltage	12V AC/DC		
:: Color Temp	3000K Warm White		
:: Beam Angle	360°		
:: Light Source	Integrated SMD LED Tower		
:: Lens	Heavy-Duty Clear PC Lens		
:: Diameter of Shade	5-3/4"	6-1/4"	6-1/4"
:: Total Height	20"	18"	12"

:: Accessories included


Stems and shades of the items on this page are not interchangeable with each other or other models




Silicon-filled  
Wire Nuts




8-1/2"  
Non-metallic Spike




3ft.  
SPT-2 18AWG  
Lead Wire



LED Tower



WET  
Location  
IP67



3  
YEAR  
WARRANTY



STEP LIGHTS WITH LED LAMPS

:: Catalog No.

AS-158-BR  
AS-158-BK

AS-159-BR  
AS-159-BK

:: Housing / Finish

Cast Aluminum,  
Bronze / Black Finish

:: Wattage

3W

:: Lumens

300LM

:: Voltage

12V AC/DC

:: Color Temp

3000K Warm White

:: Beam Angle

80°



:: Light Source

LED JC G4 Corn Lamp Bi-pin

:: Lens

Glass Lens

:: Dimensions



:: Accessories included



Silicon-filled  
Wire Nuts



3ft.  
SPT-2 18AWG  
Lead Wire



LED JC G4  
Corn Lamp Bi-pin




C18

LED STEP LIGHTS



STEP LIGHTS WITH LED LAMPS

:: Catalog No.	<b>LS-180-BZ 3" ARCHITECTURAL</b>	<b>LS-158-BZ</b>	<b>LS-158-SS</b>	<b>LS-159-BZ</b>
:: Housing / Finish	Solid Brass, Antique Bronze Finish	Solid Brass, Antique Bronze Finish	Cast Solid Brass, Stainless Steel Finish	Solid Brass, Black Finish
:: Wattage	3W			
:: Lumens	300LM			
:: Voltage	12V AC/DC			
:: Color Temp	3000K Warm White			
:: Beam Angle	80°			
:: Light Source	LED JC G4 Corn Lamp Bi-pin			
:: Lens	Glass Lens			
:: Dimensions				
:: Accessories included	 Silicon-filled Wire Nuts	 3ft. SPT-2 18AWG Lead Wire	 LED JC G4 Corn Lamp Bi-pin	 WET location  WET IP67  3 YEAR WARRANTY



LED STEP LIGHTS

:: Catalog No.

LS-124-BZ  
LS-124-AN

LS-155-BZ

LS-160-BZ  
LS-160-AN

LS-161-BZ

:: Material / Finish

Solid Brass Faceplate, Antique Bronze Finish (BZ) Aged Nickel (AN), Powder Coated Galvanized Steel Housing

:: Wattage

3W

:: Lumens

200LM

:: Voltage

12V AC/DC

:: Color Temp

3000K Warm White

:: Beam Angle

90°


:: Light Source

Integrated SMD LED Module


:: Lens

Glass, Inside Frost with Foam Gasket


:: Dimensions




Housing Depth: 3 1/2"



Housing Depth: 2 1/4"



Housing Depth: 3 1/2"



Housing Depth: 2 1/4"

:: Accessories included



Silicon-filled  
Wire Nuts



3ft.  
SPT-2 18AWG  
Lead Wire




Integrated SMD  
LED Module



C20

LED STEP LIGHTS




LED HARDSCAPE LIGHTS

:: Catalog No.	HSL-3-30K	HSL-7-30K	HSL-13-30K
:: Housing / Finish	Cast Aluminum Fixture, Stainless Steel Bracket, Aluminum Front Trim with Dark Gray Finish (Paintable)		
:: Wattage	1W	2W	3W
:: Lumens	30LM	100LM	160LM
:: Voltage	12V AC		
:: Color Temp	3000K Warm White		
:: Beam Angle	36°		
:: Light Source	LED COB Technology		
:: Lens	Built-In Glass Magnifying Lens		
:: Dimensions			
:: Accessories included	<p>3ft. SPT-2 18AWG Lead Wire</p> <p>Aluminum Dark Gray (Paintable) Trim &amp; Bracket Included</p>		



12V  
&  
120V



**SINGLE-GANG LED STEP LIGHT ENGINE FOR RECESSED TRIMS**

:: Catalog No.

SLEA-12V-30K  
SLEA-12V-50K

SLEA-120V-30K  
SLEA-120V-50K

:: Material / Finish

PVC Housing

:: Wattage

2W

:: Lumens

86LM

86LM

:: Voltage

12V AC/DC

120V AC

:: Color Temp

3000K Warm White, 5000K Cool White

:: Beam Angle

-



:: Light Source

Integrated COB LED Bar (Weatherproof) with built-in driver

:: Lens

PC Lens

:: Dimensions



Fits in  
Single Gang Switch Boxes  
(not included)

:: Accessories included



1 ft.  
SPT-2 18AWG  
Lead Wire



PVC Gasket Set  
for J-box or weatherproof box mounting




Applies to trims too

C22

LED STEP LIGHTS







**LED STEP LIGHT RECESSED TRIMS**

:: Catalog No.

SLT-A-WH (WHITE FINISH)

SLT-A-BZ (ANTIQUE BRONZE FINISH)



:: Catalog No.


SLT-A-BN (BRUSHED NICKEL FINISH)

SLT-A-ORB (OIL-RUBBED BRONZE FINISH)

:: Material

Precision-Cast Aluminum

:: Dimensions



C23

LED STEP LIGHTS



12V  
&  
120V



**SINGLE-GANG LED STEP LIGHT ENGINE**

:: Catalog No.

SLE-12V-30K  
SLE-12V-50K

SLE-120V-30K  
SLE-120V-50K

:: Material / Finish

PVC Housing W/ inside frosted PC lens

:: Wattage

3W

:: Lumens

100LM (3000K) / 118LM (5000K)

90LM (3000K) / 104LM (5000K)

:: Voltage

12V AC/DC

120V AC

:: Color Temp

3000K Warm White, 5000K Cool White

:: Beam Angle

-



:: Light Source

Integrated SMD LED Module (Weatherproof) with built-in driver

:: Lens

Glass, Inside Frost with Foam Gasket

:: Dimensions



Fits in  
Single Gang Switch Boxes  
(not included)


:: Accessories included



Applies to trims too

C24

LED STEP LIGHTS



C25

LED STEP LIGHT FACE PLATES

LED STEP LIGHTS

:: Catalog No.	SLT-LH-WH (WHITE FINISH) SLT-LH-BZ (ANTIQUER BRONZE FINISH) SLT-LH-BN (BRUSHED NICKEL FINISH) SLT-LH-ORB (OIL-RUBBED BRONZE FINISH)	SLT-F-WH (WHITE FINISH) SLT-F-BZ (ANTIQUER BRONZE FINISH) SLT-F-BN (BRUSHED NICKEL FINISH) SLT-F-ORB (OIL-RUBBED BRONZE FINISH)
----------------	--	--



:: Catalog No.	SLT-LV-WH (WHITE FINISH) SLT-LV-BZ (ANTIQUER BRONZE FINISH) SLT-LV-BN (BRUSHED NICKEL FINISH) SLT-LV-ORB (OIL-RUBBED BRONZE FINISH)	SLT-S-WH (WHITE FINISH) SLT-S-BZ (ANTIQUER BRONZE FINISH) SLT-S-BN (BRUSHED NICKEL FINISH) SLT-S-ORB (OIL-RUBBED BRONZE FINISH)
----------------	--	--

:: Material	Precision-Cast Aluminum	
-------------	-------------------------	--

:: Dimensions		
---------------	--	--

C26



**PAR36 FIXTURES**

PAR36 FIXTURES

:: Catalog No.	<b>WL-140-FBK</b>	<b>LD-001-BZ</b>
:: Housing / Finish	Fiber Glass, Black	Die-cast Brass, Antique Bronze Finish
:: Wattage	-	-
:: Lumens	Depends on lamp	Depends on lamp
:: Voltage	12V	12V
:: Color Temp	-	-
:: Beam Angle	Depends on lamp	Depends on lamp
:: Light Source	PAR36 (not included)	Shown With Westgate PAR36 Lamp (not included)
:: Dimensions		
:: Components		



12V INTEGRATED LED (IN GROUND) LIGHTS

C27

LED WELL LIGHTS

:: Catalog No.	IGL-7W-30K	IGL-3W-30K	IGL-1W-30K
:: Housing / Finish	Stainless Steel Cover, Aluminum Housing, PVC Sleeve		
:: Wattage	7W	3W	1W
:: Lumens	620LM	290LM	100LM
:: Voltage	12V AC/DC		
:: Color Temp	3000K Warm White		
:: Beam Angle	90°	45°	
:: Light Source	COB Technology (Dimmable)		
:: Lens	Glass lens		
:: Dimensions			
:: Accessories included			





C28

LED WELL LIGHTS

WELL LIGHTS WITH SLEEVE & LED LAMPS

:: Catalog No.	WL-137-BK	WL-137-BZ	WL-138-BK	WL-138-BZ	WL-138-SS
:: Housing / Finish	Cast Aluminum (Black Finish with PVC Sleeve)	Cast Brass (Antique Bronze Finish with PVC Sleeve)	Cast Aluminum (Black Finish with PVC Sleeve)	Cast Brass (Antique Bronze Finish with PVC Sleeve)	Solid Stainless Steel with PVC Sleeve
:: Wattage	5W				
:: Lumens	400LM				
:: Voltage	12V AC/DC				
:: Color Temp	3000K Warm White				
:: Beam Angle	36°				
:: Light Source	MR16 Lamp Included (WESTGATE Part Number: MR16-400L-30K-D)				
:: Lens	Flat Temp. Glass				
:: Dimensions					
:: Accessories included	<p>Silicon-filled Wire Nuts</p>		<p>3ft. SPT-2 18AWG Lead Wire</p>		<p>LED MR16 Lamp</p>



WELL LIGHTS WITH LED LAMPS

:: Catalog No.	WL-105-1-BK	WL-105-BK	WL-157-BK	WL-181-BK WL-181-BR	WL-181-BZ
:: Housing / Finish	Cast Aluminum, Black Finish		Diecast Aluminum, Black Finish	Diecast Aluminum, Black (BK) & Bronze (BR) Finish	Solid Brass Antique Bronze (BZ) Finish
:: Wattage	5W				
:: Lumens	400LM				
:: Voltage	12V AC/DC				
:: Color Temp	3000K Warm White				
:: Beam Angle	36°		60°	36°	36°
:: Light Source	MR16 lamp included (WESTGATE Part Number: MR16-400L-30K-D)				
:: Lens	Glass lens				
:: Dimensions					
:: Accessories included	<p>Silicon-filled Wire Nuts</p>		<p>3ft. SPT-2 18AWG Lead Wire</p>		<p>LED MR16 Lamp</p>
			<p>WET location</p>		<p>IP67</p>
	<p>3 YEAR WARRANTY</p> <p>Brass</p>		<p>1 YEAR WARRANTY</p> <p>Alum. &amp; FG.</p>		



**SOLID BRASS WELL LIGHTS WITH DIRECTIONAL LAMP BRACKET**

:: Catalog No.

WL-701-FGBZ

WL-705-FGBZ

WL-707-FGBZ

WL-708-FGBZ

:: Housing / Finish

Solid Brass Covers & Fiber Glass Housing / Antique Bronze Finish

:: Wattage

5W

:: Lumens

400LM

:: Voltage

12V AC/DC

:: Color Temp

3000K Warm White

:: Beam Angle

36°





:: Light Source

MR16 Lamp Included (WESTGATE Part Number: MR16-400L-30K-D)

:: Lens

Flat Temp. Glass

:: Dimensions



:: Accessories included



Silicon-filled  
Wire Nuts



3ft.  
SPT-2 18AWG  
Lead Wire



LED MR16 Lamp



Brass





LED UNDERWATER LIGHTS

C31

LED UNDERWATER LIGHTS

:: Catalog No.	UW-125-BS	UW-125-SS
:: Housing / Finish	Brass	Stainless Steel
:: Wattage	5W	
:: Lumens	400LM	
:: Voltage	12V AC/DC	
:: Color Temp	3000K Warm White	
:: Beam Angle	36°	
:: Light Source	MR16 Lamp Included (WESTGATE Part Number: MR16-400L-30K-D)	
:: Lens	Glass Lens	
:: Dimensions		
:: Accessories included		



**DUAL-TAP (12V/15V AC) LANDSCAPE TRANSFORMERS WITH TIMER & PHOTOCELL SLIDE DOOR**

C32


TRANSFORMERS

:: Catalog No.	TR-40W-DT-TPC-SS	TR-75W-DT-TPC-SS	TR-100W-DT-TPC-SS	TR-200W-DT-TPC-SS
:: Wattage	40W	75W	100W	200W
:: Finish	Stainless Steel	Stainless Steel	Stainless Steel	Stainless Steel
:: Input Voltage	120V 60Hz	120V 60Hz	120V 60Hz	120V 60Hz
:: Terminal Blocks	2	2	2	2
:: Dimensions	L 8.2" - W 3.67" - H 4.2"		L 11.35" - W 4.05" - H 4.05"	

:: Accessories included



Built-in timer  
Non-removable pins



Built-in Photocell  
Non-removable



6 Foot plug-in cord



Magnetic circuit breaker on secondary  
to protect lighting system





**MULTI-TAP (12V/13V/14V/15V AC) LANDSCAPE TRANSFORMERS  
TIMER & PHOTOCELL READY NOT INCLUDED - HINGE DOOR**

C33

TRANSFORMERS

:: Catalog No.	TR-150W-MT-SS	TR-300W-MT-SS	TR-600W-MT-SS	TR-900W-MT-SS
:: Wattage	150W	300W	600W	900W
:: Finish	Stainless Steel	Stainless Steel	Stainless Steel	Stainless Steel
:: Input Voltage	120V 60Hz	120V 60Hz	120V 60Hz	120V 60Hz
:: Terminal Blocks	2	2	2	2
:: Dimensions	L 11.4" - W 5.4" - H 5.3"	L 12.6" - W 5.9" - H 5.9"	L 18.1" - W 7.9" - H 7.9"	






:: Options			
------------	---	--	---

**PLUG-IN MECHANICAL TIMER**

**PLUG-IN DIGITAL TIMER**

**PLUG-IN PHOTOCELL**

:: Catalog No.	TR-MTMR	TR-DTMR	TR-PC
:: Description	24-Hour 3-Prong Mechanical Plug-in Timer	7-Day 3-Prong Digital Plug-in Timer	Photocell with Plug-in Molex Connector

:: Accessories included		6 Foot plug-in cord included with Transformers	   
-------------------------	---	--	---




**MR16-400L**

**MR16-500L**

**MR16-RGB**

**PAR36  
FOR ENCLOSED FIXTURES**

:: Catalog No.	MR16-400L-27K-D MR16-400L-30K-D MR16-400L-41K-D MR16-400L-50K-D	MR16-500L-C90-30K-D MR16-500L-C90-50K-D	MR16-5W-RGB	PAR36-10W-30K PAR36-10W-40K PAR36-10W-50K
:: Wattage	5W	7W	5W	10W
:: Lumens	380LM, 380LM, 390LM, 400LM	500LM, 560LM	280LM	500LM, 800LM, 600LM
:: Voltage	12V AC/DC	12V AC/DC	12V AC/DC	12V AC/DC
:: Color Temp	2700K, 3000K, 4100K, 5000K	3000K, 5000K	RGB	3000K, 4000K, 5000K
:: Beam Angle	40°	40°	36°	50°












**12V AC/DC REPLACEMENT LAMPS**

:: Catalog No.	GZ-JC-39L-27K GZ-JC-39L-30K	GZ-JC-18L-27K GZ-JC-18L-30K	GZ-JC-WP-3W-32K	GZ-S8-32K
:: Wattage	3W	2W	3W	1.4W
:: Lumens	180LM	250LM	180LM	70LM
:: Voltage	12V AC/DC	12V AC/DC	12V AC/DC	12V AC/DC
:: Color Temp	2700K, 3000K	2700K, 3000K	3200K	3200K
:: Beam Angle	360°	360°	360°	360°







C34

12V REPLACEMENT LAMPS

:: Catalog No.	:: Description	:: Note
<p><b>PVC POST</b></p>  <p>WE167-CAP</p> <p>WE167</p>	<p><b>Cat No.:</b></p> <p><b>WE167</b> Extra-long 18-1/2" PVC mounting post for ground mounted landscape fixtures.</p> <ul style="list-style-type: none"> <li>• 2-1/2" Thick Wall PVC Pipe (2-7/8" O.D.)</li> <li>• In-ground stabilizing with ribs &amp; teeth</li> <li>• Updated with brass hub</li> </ul> <p><b>WE167-CAP</b> Cap only for WE167</p>	 <p>2-3/4"</p> <p>18-1/2"</p> <p>2-1/2"</p>
<p><b>BRASS BASE</b></p>  <p>B-41-AN</p> <p>B-41</p>	<p>Surface mounting base</p> <p><b>Cat No.:</b></p> <p><b>B-41:</b></p> <ul style="list-style-type: none"> <li>• Solid Brass</li> <li>• Antique Bronze finish</li> <li>• 1/2" NPT hub</li> </ul> <p><b>B-41-AN:</b></p> <ul style="list-style-type: none"> <li>• Solid Brass</li> <li>• Aged Nickel finish</li> <li>• 1/2" NPT hub</li> </ul>	 <p>1/2" NPT</p> <p>Ø2.75 OD</p> <p>Ø2.25 BOLT PATTERN</p> <p>(3x) Ø.1875 THRU Ø.3750</p> <p>Ø1.1875</p> <p>.8125</p> <p>.3125 in</p> <p>.15625</p> <p>.3125</p>
<p><b>ALUMINUM BASE</b></p>  <p>A-41-BR</p> <p>A-41-BK</p>	<p><b>A-41-BR:</b> Surface mounting base</p> <ul style="list-style-type: none"> <li>• Cast Aluminum</li> <li>• Bronze powder coat finish</li> <li>• 1/2" NPT hub</li> </ul> <p><b>A-41-BK:</b> Surface mounting base</p> <ul style="list-style-type: none"> <li>• Cast Aluminum</li> <li>• Black powder coat finish</li> <li>• 1/2" NPT hub</li> </ul>	 <p>1/2" NPT</p> <p>Ø2.75 OD</p> <p>Ø2.25 BOLT PATTERN</p> <p>(3x) Ø.1875 THRU Ø.3750</p> <p>Ø1.1875</p> <p>.8125</p> <p>.3125 in</p> <p>.15625</p> <p>.3125</p>
<p><b>TREE BASE</b></p>  <p>A-41S</p>	<p><b>Cat No.:</b></p> <p><b>A-41S:</b> Tree mounting base. Use with bungee cords.</p> <ul style="list-style-type: none"> <li>• Cast Aluminum</li> <li>• Bronze powder coat finish</li> <li>• 1/2" NPT hub</li> <li>• With 2 mounting studs</li> </ul>	 <p>1/2" NPT</p> <p>Ø2.75 OD</p> <p>Ø2.25 BOLT PATTERN</p> <p>(3x) Ø.1875 THRU Ø.3750</p> <p>Ø1.1875</p> <p>.8125</p> <p>.3125 in</p> <p>.15625</p> <p>.3125</p>
<p><b>BUNGEE CORDS</b></p>  <p>BC-13 BC-18 BC-24 BC-32</p>	<p><b>Cat No.:</b></p> <p><b>BC-13:</b> 13" <b>BC-18:</b> 18" <b>BC-24:</b> 24" <b>BC-32:</b> 32"</p> <p>Bungee cord with hooks for mounting landscape fixtures on tree trunks. Use with A-41S base.</p>	

C35

ACCESSORIES

:: Catalog No.	:: Description	:: Note
<p><b>SPIKES</b></p>  <p>SPIKE-BG SPIKE-10 WL-SLEEVE</p>	<p>Cat No.:</p> <p><b>SPIKE-BG:</b> 8.5" PVC Spike</p> <p><b>SPIKE-10:</b> 10" PVC Spike</p> <p><b>WL-SLEEVE:</b> PVC Sleeve Kit for 4" Well Lights.</p>	 <p>3.34" 4.13" 13-1/2" 2" 2-7/8" 8-3/4" 8-1/2"</p>
<p><b>SILICON-FILLED WIRE NUTS</b> BAG OF 24</p>  <p>LSWN1 LSWN2</p>	<p>Cat No.:</p> <p><b>LSWN1:</b> Bag of 24 silicon-filled waterproof wire connectors, for up to two 14-2 + one 16-2 cables</p> <p><b>LSWN2:</b> Box of 24 silicon-filled waterproof wire connectors, for up to three 12-2 cables</p>	 <p>8.0" 1-3/8" 0.4" 5/8"</p>
<p><b>LOW-VOLTAGE CABLE</b></p>  <p>LOV-14 LOV-12 LOV-10 LOV-8</p>	<p>Cat No.:</p> <p><b>LOV-14:</b> #14 AWG (41 Strands) <b>LOV-12:</b> #12 AWG (65 Strands) <b>LOV-10:</b> #10 AWG (104 Strands) <b>LOV-8:</b> #8 AWG (168 Strands)</p> <p>500 Ft. Low-Voltage underground cable.</p> <ul style="list-style-type: none"> <li>Operating temp: -4°F to 140°F</li> <li>Suitable for outdoor lighting not exceeding 150V.</li> <li>RoHS Compliant</li> </ul>	 <p>Black PVC Insulation Jacket</p>
<p><b>PATH LIGHTING ACCESSORIES</b></p>  <p>LA-T-BZ LA-90-BZ LA-FMS21-BZ</p>	<p>Cat No.:</p> <p><b>LA-FMS21-BZ:</b> 21" Solid brass fixture mounting stem Antique bronze finish</p> <p><b>LA-T-BZ:</b> Fixture mounting "T" attachment</p> <p><b>LA-90-BZ:</b> Fixture mounting 90° elbow attachment</p> <p>Sample path light assembly shown with Westgate model LD-006-BZ (not included). Order your choice of fixture(s) separately. Use with plastic spikes included with 12V fixtures; or, order your choice of ground or surface mounting.</p>	 <p>Sample Installation with LD-006-BZ (not included)</p>

:: Catalog No.	:: Description	:: Note
<p><b>12V SNAP CONNECTOR</b></p>  <p>WE-CONN</p>	<p>Cat No.:</p> <p><b>WE-CONN</b></p> <ul style="list-style-type: none"> <li>• Main Cable: 10/2, 12/2, 14/2</li> <li>• Fixture Cable: 16/2, 18/2</li> </ul> <p>Black Color</p>	
<p><b>AREA LIGHTING REPLACEMENT PARTS</b></p>  <p>LA-STEM-RL</p> <p>LA-STEM-KNOB</p>  <p>LA-STEM-REPL-LED</p>	<p>Cat No.:</p> <p><b>LA-STEM-KNOB:</b> Replacement Knob</p> <p><b>LA-STEM-RL:</b> Replacement Glass Lens for Path Light Stem</p> <p><b>LA-STEM-REPL-LED:</b> Replacement LED Tower Also fits Pagoda Lights</p> <ul style="list-style-type: none"> <li>• 5Ft. SPT-2 18AWG Lead Wire</li> <li>• 3 Watts</li> <li>• 200 Lumens</li> <li>• 3000K</li> <li>• 12V AC/DC</li> </ul>	<p>Fit:</p>  <p>LA-STEM-KNOB</p> <p>LA-STEM-RL</p> <p>LA-STEM-REPL-LED</p>
<p><b>STEP LIGHTING REPLACEMENT LED MODULE</b></p>  <p>LS-REPL-LED</p>	<p>Cat No.:</p> <p><b>LED-REPL-LED</b> Replacement LED Module for: LS-155-BZ LS-155-BZ LS-155-BZ</p> <ul style="list-style-type: none"> <li>• 3 Watts</li> <li>• 200 Lumens</li> <li>• 3000K</li> <li>• 12V AC/DC</li> <li>• Built-in Driver</li> </ul>	<p>Fits:</p> 
<p><b>PAGODA LIGHTS REPLACEMENT GLASS</b></p>  <p>AA-145-RG AA-146-RG AA-147-RG</p>	<p>Cat No.:</p> <p><b>AA-145-RG:</b> Replacement Glass for 2-Tier Pagodas</p> <p><b>AA-146-RG:</b> Replacement Glass for 3-Tier Pagodas</p> <p><b>AA-147-RG:</b> Replacement Glass for 4-Tier Pagodas</p>	<p>Fits:</p> 