


# LED Catalog

Lamps & Fixtures • Fall 2018



LITESPANLED

selection. solutions. simplicity. [eiko.com](http://eiko.com)

# Contents

<b>Replacement Lamps .....</b>	<b>4</b>
HID Replacement Lamps.....	4
Linear Replacement Lamps.....	8
A-Line Replacement Lamps.....	12
Filament Decorative Lamps .....	15
PL CFL Replacement Lamps.....	16
PLL Replacement Lamps.....	18
BR Replacement Lamps.....	19
PAR Replacement Lamps.....	20
MR Replacement Lamps .....	22
Decorative Replacement Lamps.....	23
G4 & G9 Replacement Lamps .....	24
<b>Fixtures .....</b>	<b>25</b>
Outdoor Fixtures.....	25
High Bay Fixtures .....	28
Linear Fixtures.....	30
Troffer & Panel Fixtures .....	32
Downlight Fixtures.....	34
Canopy Fixtures.....	37
Wallpack Fixtures.....	38
Occupancy Sensors .....	40
<b>Miniatures.....</b>	<b>41</b>
Miniature LED Replacement Lamps.....	41
<b>Wire Rack Display Merchandiser.....</b>	<b>42</b>
<b>Ordering Information, Terms &amp; Conditions .....</b>	<b>43</b>



## HID Replacement Lamps

- LED HID replacement lamps for high-watt HID fixtures
- Consumes a fraction of the energy of HID systems
- Lasts many times longer than HID
- Available in a wide range of wattages and sizes
- Eliminates maintenance costs for over 10 years
- State-of-the-art LED light sources deliver ultra-high l/w
- Medium base and mogul base styles available
- Choice of color temperatures


### HID Replacement : Small 15-24W : Medium Base

Order Code	Item	Lm	W	CCT	CRI	V	Life/Hrs L70	Base	Replaces HID	Photo #
09632	LED15WPT30KMED-G7	1,875	15W	3000K	80+	100-277	50,000	E26	50W	1
09390	LED15WPT40KMED-G7	1,875	15W	4000K	80+	100-277	50,000	E26	50W	1
09391	LED15WPT50KMED-G7	1,950	15W	5000K	80+	100-277	50,000	E26	50W	1
09633	LED19WPT30KMED-G7	2,375	19W	3000K	80+	100-277	50,000	E26	75W	2
09392	LED19WPT40KMED-G7	2,375	19W	4000K	80+	100-277	50,000	E26	75W	2
09393	LED19WPT50KMED-G7	2,470	19W	5000K	80+	100-277	50,000	E26	75W	2
09634	LED24WPT30KMED-G7	3,000	24W	3000K	80+	100-277	50,000	E26	100W	3
09394	LED24WPT40KMED-G7	3,000	24W	4000K	80+	100-277	50,000	E26	100W	3
09395	LED24WPT50KMED-G7	3,120	24W	5000K	80+	100-277	50,000	E26	100W	3

### HID Replacement : Medium 27-54W : Medium Base

Order Code	Item	Lm	W	CCT	CRI	V	Life/Hrs L70	Base	Replaces HID	Photo #
09635	LED27WPT30KMED-G7	3,510	27W	3000K	80+	100-277	50,000	E26	50-125W	4
10228	LED27WPT30KMED-G8	3,650	27W	3000K	80+	100-277	50,000	E26	50-125W	4
09835	LED27WPT40KMED-347V-G7*	3,240	27W	4000K	80+	347	50,000	E26	50-125W	4
09374	LED27WPT40KMED-G7	3,510	27W	4000K	80+	100-277	50,000	E26	50-125W	4
10229	LED27WPT40KMED-G8	3,750	27W	4000K	80+	100-277	50,000	E26	50-125W	4
09836	LED27WPT50KMED-347V-G7*	3,375	27W	5000K	80+	347	50,000	E26	50-125W	4
09376	LED27WPT50KMED-G7	3,645	27W	5000K	80+	100-277	50,000	E26	50-125W	4

Continued on next page >>>



**HID Replacement : Medium 27-54W : Medium Base**

Order Code	Item	Lm	W	CCT	CRI	V	Life/Hrs L70	Base	Replaces HID	Photo #
10231	LED27WPT50KMED-G8	3,900	27W	5000K	80+	100-277	50,000	E26	50-125W	4
09637	LED36WPT30KMED-G7	4,860	36W	3000K	80+	100-277	50,000	E26	100-150W	5
10233	LED36WPT30KMED-G8	4,850	36W	3000K	80+	100-277	50,000	E26	100-150W	5
09837	LED36WPT40KMED-347V-G7	4,320	36W	4000K	80+	347	50,000	E26	100-150W	5
09378	LED36WPT40KMED-G7	4,860	36W	4000K	80+	100-277	50,000	E26	100-150W	5
10238	LED36WPT40KMED-G8	5,000	36W	4000K	80+	100-277	50,000	E26	100-150W	5
09838	LED36WPT50KMED-347V-G7	4,500	36W	5000K	80+	347	50,000	E26	100-150W	5
09380	LED36WPT50KMED-G7	4,860	36W	5000K	80+	100-277	50,000	E26	100-150W	5
10240	LED36WPT50KMED-G8	5,200	36W	5000K	80+	100-277	50,000	E26	100-150W	5
09639	LED45WPT30KMED-G7	5,850	45W	3000K	80+	100-277	50,000	E26	150-175W	6
10242	LED45WPT30KMED-G8	6,100	45W	3000K	80+	100-277	50,000	E26	150-175W	6
09839	LED45WPT40KMED-347V-G7	5,400	45W	4000K	80+	347	50,000	E26	150-175W	6
10370	LED45WPT40KMED-347V-G8	6,525	45W	4000K	80+	347	50,000	E26	150-175W	6
09382	LED45WPT40KMED-G7	5,850	45W	4000K	80+	100-277	50,000	E26	150-175W	6
10244	LED45WPT40KMED-G8	6,300	45W	4000K	80+	100-277	50,000	E26	150-175W	6
09840	LED45WPT50KMED-347V-G7	5,625	45W	5000K	80+	347	50,000	E26	150-175W	6
09384	LED45WPT50KMED-G7	6,075	45W	5000K	80+	100-277	50,000	E26	150-175W	6
10246	LED45WPT50KMED-G8	6,500	45W	5000K	80+	100-277	50,000	E26	150-175W	6
09641	LED54WPT30KMED-G7	7,020	54W	3000K	80+	100-277	50,000	E26	150-175W	7
10248	LED54WPT30KMED-G8	7,300	54W	3000K	80+	100-277	50,000	E26	150-175W	7
10371	LED54WPT40KMED-347V-G8	7,830	54W	4000K	80+	347	50,000	E26	150-175W	7
09386	LED54WPT40KMED-G7	7,020	54W	4000K	80+	100-277	50,000	E26	150-175W	7
10250	LED54WPT40KMED-G8	7,550	54W	4000K	80+	100-277	50,000	E26	150-175W	7
09388	LED54WPT50KMED-G7	7,290	54W	5000K	80+	100-277	50,000	E26	150-175W	7
10252	LED54WPT50KMED-G8	7,800	54W	5000K	80+	100-277	50,000	E26	150-175W	7

**HID Replacement : Medium 27-54W : Mogul Base**

Order Code	Item	Lm	W	CCT	CRI	V	Life/Hrs L70	Base	Replaces HID	Photo #	DLC
09636	LED27WPT30KMOG-G7	3,510	27W	3000K	80+	100-277	50,000	EX39	50-125W	4	✓
10227	LED27WPT30KMOG-G8	3,650	27W	3000K	80+	100-277	50,000	EX39	50-125W	4	✓
09829	LED27WPT40KMOG-347V-G7	3,240	27W	4000K	80+	347	50,000	E39	50-125W	4	✓
09375	LED27WPT40KMOG-G7	3,510	27W	4000K	80+	100-277	50,000	EX39	50-125W	4	✓
10230	LED27WPT40KMOG-G8	3,750	27W	4000K	80+	100-277	50,000	EX39	50-125W	4	✓
09830	LED27WPT50KMOG-347V-G7	3,375	27W	5000K	80+	347	50,000	E39	50-125W	4	✓
09377	LED27WPT50KMOG-G7	3,645	27W	5000K	80+	100-277	50,000	EX39	50-125W	4	✓
10232	LED27WPT50KMOG-G8	3,900	27W	5000K	80+	100-277	50,000	EX39	50-125W	4	✓
09638	LED36WPT30KMOG-G7	4,860	36W	3000K	80+	100-277	50,000	EX39	100-150W	5	✓
10237	LED36WPT30KMOG-G8	4,850	36W	3000K	80+	100-277	50,000	EX39	100-150W	5	✓
09831	LED36WPT40KMOG-347V-G7	4,320	36W	4000K	80+	347	50,000	E39	100-150W	5	✓
09379	LED36WPT40KMOG-G7	4,860	36W	4000K	80+	100-277	50,000	EX39	100-150W	5	✓
10239	LED36WPT40KMOG-G8	5,000	36W	4000K	80+	100-277	50,000	EX39	100-150W	5	✓
09832	LED36WPT50KMOG-347V-G7	4,500	36W	5000K	80+	347	50,000	E39	100-150W	5	✓
09381	LED36WPT50KMOG-G7	4,860	36W	5000K	80+	100-277	50,000	EX39	100-150W	5	✓
10241	LED36WPT50KMOG-G8	5,200	36W	5000K	80+	100-277	50,000	EX39	100-150W	5	✓
09640	LED45WPT30KMOG-G7	5,850	45W	3000K	80+	100-277	50,000	EX39	150-175W	6	✓

Continued on next page >>>



**HID Replacement : Medium 27-54W : Mogul Base**

Order Code	Item	Lm	W	CCT	CRI	V	Life/Hrs L70	Base	Replaces HID	Photo #	DLC
10243	LED45WPT30KMOG-G8	6,100	45W	3000K	80+	100-277	50,000	EX39	150-175W	6	✓
09833	LED45WPT40KMOG-347V-G7	5,400	45W	4000K	80+	347	50,000	E39	150-175W	6	✓
10372	LED45WPT40KMOG-347V-G8	6,525	45W	4000K	80+	347	50,000	EX39	150-175W	6	✓
09383	LED45WPT40KMOG-G7	5,850	45W	4000K	80+	100-277	50,000	EX39	150-175W	6	✓
10245	LED45WPT40KMOG-G8	6,300	45W	4000K	80+	100-277	50,000	EX39	150-175W	6	✓
09834	LED45WPT50KMOG-347V-G7	5,625	45W	5000K	80+	347	50,000	E39	150-175W	6	✓
09385	LED45WPT50KMOG-G7	6,075	45W	5000K	80+	100-277	50,000	EX39	150-175W	6	✓
10247	LED45WPT50KMOG-G8	6,500	45W	5000K	80+	100-277	50,000	EX39	150-175W	6	✓
09642	LED54WPT30KMOG-G7	7,020	54W	3000K	80+	100-277	50,000	EX39	150-175W	7	✓
10249	LED54WPT30KMOG-G8	7,300	54W	3000K	80+	100-277	50,000	EX39	150-175W	7	✓
09428	LED54WPT40KMOG-347V-G7	7,020	54W	4000K	80+	347	50,000	E39	150-175W	7	✓
10373	LED54WPT40KMOG-347V-G8	7,830	54W	4000K	80+	347	50,000	EX39	150-175W	7	✓
09387	LED54WPT40KMOG-G7	7,020	54W	4000K	80+	100-277	50,000	EX39	150-175W	7	✓
10251	LED54WPT40KMOG-G8	7,550	54W	4000K	80+	100-277	50,000	EX39	150-175W	7	✓
09450	LED54WPT50KMOG-347V-G7	7,290	54W	5000K	80+	347	50,000	E39	150-175W	7	✓
10374	LED54WPT50KMOG-347V-G8	8,100	54W	5000K	80+	347	50,000	EX39	150-175W	7	✓
09389	LED54WPT50KMOG-G7	7,290	54W	5000K	80+	100-277	50,000	EX39	150-175W	7	✓
10253	LED54WPT50KMOG-G8	7,800	54W	5000K	80+	100-277	50,000	EX39	150-175W	7	✓

**HID Replacement : Large : Mogul Base**

Order Code	Item	Lm	W	CCT	CRI	V	Life/Hrs L70	Base	Replaces HID	Photo #	DLC
09827	LED80WPT40KMOG-347V-G8	10,400	80W	4000K	80+	347	50,000	E39	250W	8	✓
09346	LED80WPT40KMOG-G6	10,400	80W	4000K	80+	100-277	50,000	EX39	250W	8	✓
10260	LED80WPT40KMOG-G8	10,400	80W	5000K	80+	100-277	50,000	EX39	250W	8	✓
09828	LED80WPT50KMOG-347V-G8	10,800	80W	4000K	80+	347	50,000	E39	250W	8	✓
09347	LED80WPT50KMOG-G6	10,400	80W	5000K	80+	100-277	50,000	EX39	250W	8	✓
10261	LED80WPT50KMOG-G8	10,560	80W	5000K	80+	100-277	50,000	EX39	250W	8	✓
09661	LED100WPT30KMOG-G6	12,000	100W	3000K	80+	100-277	50,000	EX39	400W	9	✓
10254	LED100WPT30KMOG-G8	12,800	100W	3000K	80+	100-277	50,000	EX39	400W	9	✓
09825	LED100WPT40KMOG-347V-G8	13,000	100W	4000K	80+	347	50,000	E39	400W	9	✓
09348	LED100WPT40KMOG-G6	13,000	100W	4000K	80+	100-277	50,000	EX39	400W	9	✓
10255	LED100WPT40KMOG-G8	13,000	100W	4000K	80+	100-277	50,000	EX39	400W	9	✓
09826	LED100WPT50KMOG-347V-G8	13,500	100W	5000K	80+	347	50,000	E39	400W	9	✓
09153	LED100WPT50KMOG-G6	13,300	100W	5000K	80+	100-277	50,000	EX39	400W	9	✓
10256	LED100WPT50KMOG-G8	13,200	100W	5000K	80+	100-277	50,000	EX39	400W	9	✓
09349	LED120WPT40KMOG-G6	15,600	120W	4000K	80+	100-277	50,000	EX39	600W	10	✓
09154	LED120WPT50KMOG-G6	15,960	120W	5000K	80+	100-277	50,000	EX39	600W	10	✓
10258	LED120WPT40KMOG-G8	15,600	120W	4000K	80+	100-277	50,000	EX39	600W	10	✓
10259	LED120WPT50KMOG-G8	15,840	120W	5000K	80+	100-277	50,000	EX39	600W	10	✓



### HID Replacement : Horizontal : Medium and Mogul Base

Order Code	Item	Lm	W	CCT	CRI	V	Life/Hrs L70	Base	Replaces HID	Photo #	DLC
09652	LED20WPT/180/30KMED-G7	2,700	20W	3000K	80+	100-277	50,000	E26	100W	11	
09653	LED20WPT/180/40KMED-G7	2,700	20W	4000K	80+	100-277	50,000	E26	100W	11	
09402	LED20WPT/180/40KMOG-G7	2,700	20W	4000K	80+	100-277	50,000	E39	100W	11	✓
09654	LED20WPT/180/50KMED-G7	2,800	20W	5000K	80+	100-277	50,000	E26	100W	11	
09403	LED20WPT/180/50KMOG-G7	2,800	20W	5000K	80+	100-277	50,000	E39	100W	11	✓
09655	LED30WPT/180/30KMED-G7	4,050	30W	3000K	80+	100-277	50,000	E26	175W	12	
09656	LED30WPT/180/40KMED-G7	4,050	30W	4000K	80+	100-277	50,000	E26	175W	12	
09404	LED30WPT/180/40KMOG-G7	4,050	30W	4000K	80+	100-277	50,000	E39	175W	12	✓
09657	LED30WPT/180/50KMED-G7	4,050	30W	5000K	80+	100-277	50,000	E26	175W	12	
09405	LED30WPT/180/50KMOG-G7	4,050	30W	5000K	80+	100-277	50,000	E39	175W	12	✓
09658	LED40WPT/180/30KMED-G7	5,400	40W	3000K	80+	100-277	50,000	E26	250W	13	
09659	LED40WPT/180/40KMED-G7	5,400	40W	4000K	80+	100-277	50,000	E26	250W	13	
09406	LED40WPT/180/40KMOG-G7	5,600	40W	4000K	80+	100-277	50,000	E26	250W	13	✓
09660	LED40WPT/180/50KMED-G7	5,600	40W	5000K	80+	100-277	50,000	E26	250W	13	
09407	LED40WPT/180/50KMOG-G7	5,600	40W	5000K	80+	100-277	50,000	E26	250W	13	✓

### HID Replacement : Area Light : Mogul Base

Order Code	Item	Lm	W	CCT	CRI	V	Life/Hrs L70	Base	Replaces HID	Photo #	DLC
09643	LED80WAL30KMOG-G7	10,400	80W	3000K	80+	100-277	50,000	EX39	400W	14	✓
09644	LED80WAL40KMOG-G7	10,400	80W	4000K	80+	100-277	50,000	EX39	400W	14	✓
09645	LED80WAL50KMOG-G7	10,800	80W	5000K	80+	100-277	50,000	EX39	400W	14	✓
09646	LED110WAL30KMOG-G7	14,300	110W	3000K	80+	100-277	50,000	EX39	600W	14	✓
09647	LED110WAL40KMOG-G7	14,300	110W	4000K	80+	100-277	50,000	EX39	600W	14	✓
09648	LED110WAL50KMOG-G7	14,850	110W	5000K	80+	100-277	50,000	EX39	600W	14	✓

### HID Replacement : Highbay : Mogul Base

Order Code	Item	Lm	W	CCT	CRI	V	Life/Hrs L70	Base	Replaces HID	Photo #	DLC
10097	LED75WHB50KMOG-G8	9,000	75W	5000K	80+	120-277	50,000	E39	150W	15	✓
09698	LED115WB40KMOG-G7	14,950	115W	4000K	80+	100-277	50,000	EX39	400W	16	✓
09699	LED115WB50KMOG-G7	15,525	115W	5000K	80+	100-277	50,000	EX39	400W	16	✓
10098	LED120WHB50KMOG-G8	14,000	120W	5000K	80+	120-277	50,000	E39	250W	15	✓

### HID Replacement : Temporary Work Light

Order Code	Item	Lm	W	CCT	CRI	V	Life/Hrs L70	Base	Replaces HID	Photo #	DLC
09649	TMP-3C-50K-U	6,900	60W	5000K	80+	120	50,000	Hook	250W	17	✓
09650	TMP-4C-50K-U	9,200	80W	5000K	80+	120	50,000	Hook	320W	17	✓
09651	TMP-5C-50K-U	11,500	100W	5000K	80+	120	50,000	Hook	400W	17	✓





## Linear Replacement Lamps

- Solid state replacement for T5, T8 & T12 linear fluorescent
- Available in line voltage/ballast bypass, direct fit, and hybrid dual mode for a range of installation options
- Ultra-high performance LEDs deliver exceptional lpw
- Available in shatterproof nano-polycarbonate and PET-coated versions
- NSF or ETL Sanitation Listed for commercial foodservice equipment

### T8 Linear : Dual Mode

Order Code	Item	Length	Lm	Nominal Lamp W	CCT	CRI	V (Ballast Dependent)	Bm	Life/Hrs L70	Photo #	DLC
10101	LED12WT8/48/835-G8DM	4'	1,800	12W	3500K	80+	120-277	190°	50,000	1	✓
10102	LED12WT8/48/840-G8DM	4'	1,900	12W	4000K	80+	120-277	190°	50,000	1	✓
10103	LED12WT8/48/850-G8DM	4'	1,900	12W	5000K	80+	120-277	190°	50,000	1	✓
09517	LED15WT8F/48/835K-G7DM	4'	1,800	15W	3500K	80+	120-277	220°	50,000	1	
09291	LED15WT8F/48/840K-G7DM	4'	1,800	15W	4000K	80+	120-277	220°	50,000	1	
09292	LED15WT8F/48/850K-G7DM	4'	1,800	15W	5000K	80+	120-277	220°	50,000	1	

### T8 Linear : Direct Fit

Order Code	Item	Length	Lm	Nominal Lamp W	CCT	CRI	V (Ballast Dependent)	Bm	Life/Hrs L70	Photo #	DLC
60440	LED8WT8/24/835-G7DR	2'	1,200	8W	3500K	80+	120-277	220°	50,000	1	✓
60441	LED8WT8/24/840-G7DR	2'	1,250	8W	4000K	80+	120-277	220°	50,000	1	✓
60442	LED8WT8/24/850-G7DR	2'	1,250	8W	5000K	80+	120-277	220°	50,000	1	✓
10303	LED10WT8F/36/835-G8DR	3'	1,450	10W	3500K	80+	120-277	220°	50,000	2	✓
10262	LED10WT8F/36/840-G8DR	3'	1,450	10W	4000K	80+	120-277	220°	50,000	2	✓
10263	LED10WT8F/36/850-G8DR	3'	1,450	10W	5000K	80+	120-277	220°	50,000	2	✓
09785	LED10.5WT8F/36/835-G7DR	3'	1,400	11W	3500K	80+	120-277	220°	50,000	1	✓
09562	LED11.5WT8/48/835-PET-G7DR	4'	1,700	12W	3500K	80+	120-277	220°	50,000	1	✓
09563	LED11.5WT8/48/840-PET-G7DR	4'	1,800	12W	4000K	80+	120-277	220°	50,000	1	✓
09564	LED11.5WT8/48/850-PET-G7DR	4'	1,800	12W	5000K	80+	120-277	220°	50,000	1	✓

Continued on next page >>>



### T8 Linear : Direct Fit

Order Code	Item	Length	Lm	Nominal Lamp W	CCT	CRI	V (Ballast Dependent)	Bm	Life/Hrs L70	Photo #	DLC
09931	LED12WT8/48/835-G8DR	4'	1,700	12W	3500K	80+	120-277	220°	50,000	2	✓
09932	LED12WT8/48/840-G8DR	4'	1,800	12W	4000K	80+	120-277	220°	50,000	2	✓
09933	LED12WT8/48/850-G8DR	4'	1,800	12W	5000K	80+	120-277	220°	50,000	2	✓
09934	LED15WT8/48/835-G8DR	4'	2,100	15W	3500K	80+	120-277	220°	50,000	2	✓
09672	LED15WT8/48/835-PET-G7DR	4'	2,100	15W	3500K	80+	120-277	220°	50,000	1	✓
09935	LED15WT8/48/840-G8DR	4'	2,200	15W	4000K	80+	120-277	220°	50,000	2	✓
09673	LED15WT8/48/840-PET-G7DR	4'	2,200	15W	4000K	80+	120-277	220°	50,000	1	✓
09561	LED15WT8/48/850-G7DR	4'	2,200	15W	5000K	80+	120-277	220°	50,000	1	✓
09936	LED15WT8/48/850-G8DR	4'	2,200	15W	5000K	80+	120-277	220°	50,000	2	✓
09167	LED18T8F/48/835-G6DR	4'	1,800	14W	3500K	80+	120-277	220°	50,000	5	
09302	LED22T8F/48/835-G6DR-M*	4'	2,100	17W	3500K	80+	120-277	220°	50,000	1	
09290	LED22T8F/48/840-G6DR-M*	4'	2,200	17W	4000K	80+	120-277	220°	50,000	1	

### T8 U-Bend : Direct Fit

Order Code	Item	Length	Lm	Nominal Lamp W	CCT	CRI	V (Ballast Dependent)	Bm	Life/Hrs L70	Photo #	DLC
10094	LED11.5WT8F/U1/835-G8DR	U1	1,700	12W	3500K	80+	120-277	220°	50,000	3	✓
10095	LED11.5WT8F/U1/840-G8DR	U1	1,800	12W	4000K	80+	120-277	220°	50,000	3	✓
10096	LED11.5WT8F/U1/850-G8DR	U1	1,800	12W	5000K	80+	120-277	220°	50,000	3	✓
10093	LED11.5WT8F/U6/835-G8DR	U6	1,700	12W	3500K	80+	120-277	220°	50,000	4	
10063	LED11.5WT8F/U6/840-G8DR	U6	1,800	12W	4000K	80+	120-277	220°	50,000	4	
10068	LED11.5WT8F/U6/850-G8DR	U6	1,800	12W	5000K	80+	120-277	220°	50,000	4	

### T8 Linear : Bypass/Line Voltage : Nano Polycarbonate

Order Code	Item	Length	Lm	W	CCT	CRI	V	Bm	Life/Hrs L70	Photo #	DLC
09736	LED14WT8/P/48/835-G8D	4'	1,700	14W	3500K	80+	120-277	210°	50,000	5	✓
09735	LED14WT8/P/48/840-G8D	4'	1,800	14W	4000K	80+	120-277	210°	50,000	5	✓
09734	LED14WT8/P/48/850-G8D	4'	1,800	14W	5000K	80+	120-277	210°	50,000	5	✓
09362	LED17WT8/P/48/835-G7D	4'	2,100	17W	3500K	80+	120-277	210°	50,000	5	✓
09733	LED17WT8/P/48/835-G8D	4'	2,100	17W	3500K	80+	120-277	210°	50,000	5	✓
09732	LED17WT8/P/48/840-G8D	4'	2,200	17W	4000K	80+	120-277	210°	50,000	5	✓
09731	LED17WT8/P/48/850-G8D	4'	2,200	17W	5000K	80+	120-277	210°	50,000	5	✓
09897	T8-PF-05C-40K-U †	4'	2,850	20W	5000K	80+	100-277	120°	50,000	5	✓
09418	T8-PF-05C-50K-U †	4'	2,850	20W	5000K	80+	100-277	120°	50,000	5	✓

### T8 Linear : Bypass/Line Voltage

Order Code	Item	Length	Lm	W	CCT	CRI	V	Bm	Life/Hrs L70	Photo #	DLC
09322	LED9WT8F/24/835K-G7D	2'	1,100	9W	3500K	80+	120-277	220°	50,000	1	✓
09323	LED9WT8F/24/840K-G7D	2'	1,150	9W	4000K	80+	120-277	220°	50,000	1	✓
09324	LED9WT8F/24/850K-G7D	2'	1,150	9W	5000K	80+	120-277	220°	50,000	1	✓
09666	LED11.5WT8/48/835-G7D	4'	1,700	12W	3500K	80+	120-277	210°	50,000	1	✓
09669	LED11.5WT8/48/835-PET-G7D	4'	1,700	12W	3500K	80+	120-277	210°	50,000	1	✓

Continued on next page >>>





**T8 Linear** : Bypass/Line Voltage

Order Code	Item	Length	Lm	W	CCT	CRI	V	Bm	Life/Hrs L70	Photo #	DLC
09667	LED11.5WT8/48/840-G7D	4'	1,800	12W	4000K	80+	120-277	210°	50,000	1	✓
09670	LED11.5WT8/48/840-PET-G7D	4'	1,800	12W	4000K	80+	120-277	210°	50,000	1	✓
09668	LED11.5WT8/48/850-G7D	4'	1,800	12W	5000K	80+	120-277	210°	50,000	1	✓
09671	LED11.5WT8/48/850-PET-G7D	4'	1,800	12W	5000K	80+	120-277	210°	50,000	1	✓
09319	LED12WT8F/36/835K-G7D	3'	1,400	12W	3500K	80+	120-277	220°	50,000	1	
09320	LED12WT8F/36/840K-G7D	3'	1,450	12W	4000K	80+	120-277	220°	50,000	1	
09321	LED12WT8F/36/850K-G7D	3'	1,450	12W	5000K	80+	120-277	220°	50,000	1	
09288	LED15WT8F/48/835K-G7D	4'	1,700	15W	3500K	80+	120-277	220°	50,000	1	✓
09278	LED15WT8F/48/840K-G7D	4'	1,800	15W	4000K	80+	120-277	220°	50,000	1	✓
09279	LED15WT8F/48/850K-G7D	4'	1,800	15W	5000K	80+	120-277	220°	50,000	1	✓
09396	LED18WT8F/48/835-G7D	4'	2,100	18W	3500K	80+	120-277	210°	50,000	1	✓
09893	LED18WT8F/48/835-G7D-347V*	4'	2,100	18W	3500K	80+	347	210°	50,000	1	✓
09397	LED18WT8F/48/840-G7D	4'	2,200	18W	4000K	80+	120-277	210°	50,000	1	✓
09891	LED18WT8F/48/840-G7D-347V*	4'	2,200	18W	4000K	80+	347	210°	50,000	1	✓
09398	LED18WT8F/48/850-G7D	4'	2,200	18W	5000K	80+	120-277	210°	50,000	1	✓
09894	LED18WT8F/48/850-G7D-347V*	4'	2,200	18W	5000K	80+	347	210°	50,000	1	✓

**T8 U-Bend** : Bypass/Line Voltage

Order Code	Item	Length	Lm	W	CCT	CRI	V	Bm	Life/Hrs L70	Photo #	DLC
10090	LED18WT8F/U6/835-G8D	U6	2,200	18W	3500K	80+	120-277	210°	50,000	4	
10091	LED18WT8F/U6/840-G8D	U6	2,200	18W	4000K	80+	120-277	210°	50,000	4	
10092	LED18WT8F/U6/850-G8D	U6	2,200	18W	5000K	80+	120-277	210°	50,000	4	
09789	LED15WT8F/U6/835-G7D	U6	1,700	15W	3500K	80+	120-277	210°	50,000	4	✓
09790	LED15WT8F/U6/840-G7D	U6	1,800	15W	4000K	80+	120-277	210°	50,000	4	✓
09791	LED15WT8F/U6/850-G7D	U6	1,800	15W	5000K	80+	120-277	210°	50,000	4	✓
09113	LED18T8F/U6/835-G5DR	U6	1,800	12W	3500K	80+	120-277	220°	50,000	4	

**T8 8' Linear** : Bypass/Line Voltage

Order Code	Item	Length	Lm	W	CCT	CRI	V	Bm	Life/Hrs L70	Photo #	DLC
09567	LED43WT8/96/840-DBL-G7D	8'	5,500	43W	4000K	80+	120-277	210°	50,000	6	✓
10104	LED43WT8/96/840-R17D-G8	8'	5,500	43W	4000K	80+	120-277	210°	50,000	7	
09568	LED43WT8/96/850-DBL-G7D	8'	5,500	43W	5000K	80+	120-277	210°	50,000	6	✓
10105	LED43WT8/96/850-R17D-G8	8'	5,500	43W	5000K	80+	120-277	210°	50,000	7	

\$1500 minimum total order required for paid freight when purchasing any 8' T8 products. Product ships on 8' pallet in case quantities only.

**T8 Double-Ended Linear** : Bypass/Line Voltage

Order Code	Item	Length	Lm	W	CCT	CRI	V	Bm	Life/Hrs L70	Photo #	DLC
09598	LED9WT8/24/840-DBL-G7D	2'	1,150	9W	4000K	80+	120-277	210°	50,000	8	✓
09599	LED9WT8/24/850-DBL-G7D	2'	1,150	9W	5000K	80+	120-277	210°	50,000	8	✓
09600	LED12WT8/36/835-DBL-G7D	3'	1,400	12W	3500K	80+	120-277	210°	50,000	8	
09601	LED12WT8/36/840-DBL-G7D	3'	1,450	12W	4000K	80+	120-277	210°	50,000	8	

Continued on next page >>>



### T8 Double-Ended Linear : Bypass/Line Voltage

Order Code	Item	Length	Lm	W	CCT	CRI	V	Bm	Life/Hrs L70	Photo #	DLC
09602	LED12WT8/36/850-DBL-G7D	3'	1,450	12W	5000K	80+	120-277	210°	50,000	8	
09594	LED14WT8/48/835-DBL-G7D	4'	1,700	14W	3500K	80+	120-277	210°	50,000	8	✓
10437	LED12WT8/48/835-DBL-G8D	4'	1,800	12W	3500K	80+	120-277	210°	50,000	8	✓
10435	LED12WT8/48/840-DBL-G8D	4'	1,800	12W	4000K	80+	120-277	210°	50,000	8	✓
10438	LED12WT8/48/850-DBL-G8D	4'	1,800	12W	5000K	80+	120-277	210°	50,000	8	✓
09595	LED14WT8/48/840-DBL-G7D	4'	1,800	14W	4000K	80+	120-277	210°	50,000	8	✓
09603	LED14WT8/48/850-DBL-G7D	4'	1,800	14W	5000K	80+	120-277	210°	50,000	8	✓
10469	LED15WT8/48/835-DBL-G8D	4'	2,200	15W	3500K	80+	120-277	210°	50,000	8	✓
10436	LED15WT8/48/840-DBL-G8D	4'	2,200	15W	4000K	80+	120-277	210°	50,000	8	✓
10470	LED15WT8/48/850-DBL-G8D	4'	2,200	15W	5000K	80+	120-277	210°	50,000	8	✓
09604	LED17WT8/48/835-DBL-G7D	4'	2,100	17W	3500K	80+	120-277	210°	50,000	8	✓
09605	LED17WT8/48/840-DBL-G7D	4'	2,200	17W	4000K	80+	120-277	210°	50,000	8	✓
09606	LED17WT8/48/850-DBL-G7D	4'	2,200	17W	5000K	80+	120-277	210°	50,000	8	✓

### T5 Linear : Direct Fit

Order Code	Item	Length	Lm	Nominal Lamp W	CCT	CRI	V (Ballast Dependent)	Bm	Life/Hrs L70	Photo #	DLC
10128	LED11WT5HO/22/835-G8DR	2'	1,350	11W	3500K	80+	120-277	185°	50,000	9	
10129	LED11WT5HO/22/840-G8DR	2'	1,400	11W	5000K	80+	120-277	185°	50,000	9	
10039	LED11WT5HO/22/850-G8DR	2'	1,400	11W	5000K	80+	120-277	185°	50,000	9	
09553	LED11WT5HO/22/835-G7DR	2'	1,350	11W	3500K	80+	120-277	185°	50,000	9	
09556	LED12.5WT5HE/46/835-G7DR	4'	1,700	13W	3500K	80+	120-277	185°	50,000	9	
09557	LED12.5WT5HE/46/840-G7DR	4'	1,800	13W	4000K	80+	120-277	185°	50,000	9	
09558	LED12.5WT5HE/46/850-G7DR	4'	1,800	13W	5000K	80+	120-277	185°	50,000	9	
09928	LED25WT5HO/46/835-G8DR	4'	3,300	25W	3500K	80+	120-277	185°	50,000	9	✓
09930	LED25WT5HO/46/840-G8DR	4'	3,300	25W	4000K	80+	120-277	185°	50,000	9	✓
09900	LED25WT5HO/46/850-G8DR	4'	3,500	25W	5000K	80+	120-277	185°	50,000	9	✓

### T5 Linear : Bypass/Line Voltage

Order Code	Item	Length	Lm	W	CCT	CRI	V	Bm	Life/Hrs L70	Photo #	DLC
09949	LED25WT5HO/46/835-G8D	4'	3,300	25W	3500K	80+	120-277	185°	50,000	9	✓
09947	LED25WT5HO/46/840-G8D	4'	3,500	25W	4000K	80+	120-277	185°	50,000	9	✓
09948	LED25WT5HO/46/850-G8D	4'	3,500	25W	5000K	80+	120-277	185°	50,000	9	✓
10047	LED25WT5HO/46/835-G8D-347V*	4'	3,375	25W	3500K	80+	120-277	185°	50,000	9	✓
10048	LED25WT5HO/46/840-G8D-347V*	4'	3,375	25W	4000K	80+	120-277	185°	50,000	9	✓
10049	LED25WT5HO/46/850-G8D-347V*	4'	3,375	25W	5000K	80+	120-277	185°	50,000	9	✓





## A-Line Replacement Lamps

- Direct replacement for incandescent A lamps
- 300° omni beam angle is ideal for table lamps, wall sconces, and luminous globe fixtures
- 80% more efficient and 30x longer life than incandescent
- Compatible with a wide array of dimmers
- Instant-on with no warm up, unlike CFLs
- Available in 2700K, 3000K, and 4000K CCT
- Shatter-resistant for reduced risk of injury and breakage

### A15 Replacement

Order Code	Item	Lm	W	CCT	CRI	V	Life/Hrs L70	Base	Replaces Incan.	Photo #	ES
09976	LED5WA15/OMN/BLUE-G8	-	5W	Blue	-	120V	10,000	E26	-	1	
09981	LED5WA15/OMN/RED-G8	-	5W	Red	-	120V	10,000	E26	-	2	★
09973	LED5WA15/OMN/YELLOW-G8	-	5W	Yellow	-	120V	10,000	E26	-	3	★
10057	LED8WA15/OMN/827-DIM-G8	800	8W	2700K	80+	120V	25,000	E26	60W	4	★
10058	LED8WA15/OMN/830-DIM-G8	800	8W	3000K	80+	120V	25,000	E26	60W	4	★
10059	LED8WA15/OMN/840-DIM-G8	800	8W	4000K	80+	120V	25,000	E26	60W	4	★

### A19 Replacement

Order Code	Item	Lm	W	CCT	CRI	V	Life/Hrs L70	Base	Replaces Incan.	Photo #	ES
09882	LED6WA19/OMN/827-DIM-G8	480	6W	2700K	80+	120V	25,000	E26	40W	5	★
10274	LED6WA19/OMN/827-DIM-G9	480	6W	2700K	80+	120V	25,000	E26	40W	5	
09887	LED6WA19/OMN/827-G8	480	6W	2700K	80+	120V	15,000	E26	40W	5	★
60421	LED6WA19/OMN/827K-DIM-G7 2PK	480	6W	2700K	80+	120V	15,000	E26	40W	5	
10276	LED6WA19/OMN/830-DIM-G9	480	6W	3000K	80+	120V	25,000	E26	40W	5	★
09750	LED6WA19/OMN/830-G8*	480	6W	3000K	80+	120V	15,000	E26	40W	5	★
09749	LED6WA19/OMN/840-DIM-G8	480	6W	4000K	80+	120V	25,000	E26	40W	5	★
10277	LED6WA19/OMN/840-DIM-G9	480	6W	4000K	80+	120V	25,000	E26	40W	5	★
09751	LED6WA19/OMN/840-G8*	480	6W	4000K	80+	120V	15,000	E26	40W	5	★
09895	LED9WA19/OMN/827-DIM-G8	800	9W	2700K	80+	120V	25,000	E26	60W	5	★

Continued on next page >>>



## A19 Replacement

Order Code	Item	Lm	W	CCT	CRI	V	Life/Hrs L70	Base	Replaces Incan.	Photo #	ES
10283	LED9WA19/OMN/827-DIM-G9	800	9W	2700K	80+	120V	25,000	E26	60W	5	★
09974	LED9WA19/OMN/827-GU24-DIM-G8	1,100	9W	2700K	80+	120V	15,000	GU24	75W	6	★
10284	LED9WA19/OMN/827-GU24-DIM-G9	800	9W	2700K	80+	120V	25,000	GU24	60W	6	
09896	LED9WA19/OMN/830-DIM-G8	800	9W	3000K	80+	120V	25,000	E26	60W	5	★
10285	LED9WA19/OMN/830-DIM-G9	800	9W	3000K	80+	120V	25,000	E26	60W	5	★
09975	LED9WA19/OMN/830-GU24-DIM-G8	1,100	9W	3000K	80+	120V	15,000	GU24	75W	6	★
10286	LED9WA19/OMN/830-GU24-DIM-G9	800	9W	3000K	80+	120V	25,000	GU24	60W	6	
09752	LED9WA19/OMN/840-DIM-G8	800	9W	4000K	80+	120V	25,000	E26	60W	5	★
10287	LED9WA19/OMN/840-DIM-G9	800	9W	4000K	80+	120V	25,000	E26	60W	5	★
10108	LED9WA19/OMN/840-GU24-DIM-G8	1,100	9W	4000K	80+	120V	15,000	GU24	60W	6	★
10288	LED9WA19/OMN/840-GU24-DIM-G9	800	9W	4000K	80+	120V	25,000	GU24	60W	6	
10289	LED9WA19/OMN/850-DIM-G9	800	9W	5000K	80+	120V	25,000	E26	60W	5	★
09889	LED9.5WA19/OMN/827-G8	800	10W	2700K	80+	120V	15,000	E26	60W	5	★
09753	LED9.5WA19/OMN/830-G8	800	10W	3000K	80+	120V	15,000	E26	60W	5	★
09941	LED9.5WA19/OMN/840-G8	800	10W	4000K	80+	120V	15,000	E26	60W	5	★
09885	LED11WA19/OMN/827-DIM-G8	1,100	11W	2700K	80+	120V	25,000	E26	75W	5	★
10122	LED11WA19/OMN/827-GU24-DIM-G8	1,100	11W	2700K	80+	120V	15,000	GU24	75W	6	★
10014	LED11WA19/OMN/830-GU24-DIM-G8	1,100	11W	3000K	80+	120V	15,000	GU24	75W	6	★
10100	LED11WA19/OMN/840-GU24-DIM-G8	1,100	11W	4000K	80+	120V	15,000	GU24	75W	6	★
10266	LED11WA19/OMN/827-GU24-DIM-G9	1,100	11W	2700K	80+	120V	25,000	GU24	75W	6	★
60430	LED11WA19/OMN/827K-DIM-G7 2PK	1,100	11W	2700K	80+	120V	15,000	E26	75W	5	★
09942	LED11WA19/OMN/830-DIM-G8	1,100	11W	3000K	80+	120V	25,000	E26	75W	5	★
10267	LED11WA19/OMN/830-GU24-DIM-G9	1,100	11W	3000K	80+	120V	25,000	GU24	75W	6	★
09943	LED11WA19/OMN/840-DIM-G8	1,100	11W	4000K	80+	120V	25,000	E26	75W	5	★
10268	LED11WA19/OMN/840-GU24-DIM-G9	1,100	11W	3000K	80+	120V	25,000	GU24	75W	6	★
10061	LED11WA19/OMN/850-DIM-G8	1,100	11W	5000K	80+	120V	25,000	E26	75W	5	★
09886	LED15WA19/OMN/827-DIM-G8	1,600	15W	2700K	80+	120V	25,000	E26	100W	5	★
10269	LED15WA19/OMN/827-DIM-G9	1,600	15W	2700K	80+	120V	25,000	E26	100W	5	★
09944	LED15WA19/OMN/830-DIM-G8	1,600	15W	3000K	80+	120V	25,000	E26	100W	5	★
10270	LED15WA19/OMN/830-DIM-G9	1,600	15W	3000K	80+	120V	25,000	E26	100W	5	★
10125	LED15WA19/OMN/830-GU24-DIM-G8*	1,600	15W	3000K	80+	120V	25,000	GU24	100W	6	
09945	LED15WA19/OMN/840-DIM-G8	1,600	15W	4000K	80+	120V	25,000	E26	100W	5	★
10271	LED15WA19/OMN/840-DIM-G9	1,600	15W	4000K	80+	120V	25,000	E26	100W	5	★
09946	LED15WA19/OMN/850-DIM-G8	1,600	15W	5000K	80+	120V	25,000	E26	100W	5	★
10273	LED15WA19/OMN/850-DIM-G9	1,600	15W	5000K	80+	120V	25,000	E26	100W	5	★

## Advantage™ A19/A21

Order Code	Item	Lm	W	CCT	CRI	V	Life/Hrs L70	Base	Replaces Incan.	Photo #
09503	LED6WA19/ADV/827-G7A 2PK	450	6W	2700K	80+	120V	15,000	E26	40W	5
09504	LED6WA19/ADV/830-G7A 2PK	450	6W	3000K	80+	120V	15,000	E26	40W	5
10106	LED6WA19/ADV/840-G8	450	6W	4000K	80+	120V	10,000	E26	40W	5
09461	LED6WA19/ADV/850-DIM-G7 2PK	440	6W	5000K	80+	120V	15,000	E26	40W	5
90029	LED7WA19/240/850K-DIM-G4A	420	7W	5000K	80+	120V	25,000	E26	60W	5
08886	LED7WA19/240/830K-DIM-G5A	420	7W	3000K	80+	120V	25,000	E26	60W	5
09506	LED9WA19/ADV/827-DIM-G7A 2PK	750	9W	2700K	80+	120V	15,000	E26	60W	5

Continued on next page >>>



**Advantage™ A19/A21**

Order Code	Item	Lm	W	CCT	CRI	V	Life/Hrs L70	Base	Replaces Incan.	Photo #
<b>09987</b>	LED9WA19/ADV/830-DIM-G8	750	9W	3000K	80+	120V	10,000	E26	60W	5
<b>10281</b>	LED9WA19/ADV/830-DIM-G9	750	9W	3000K	80+	120V	15,000	E26	60W	5
<b>10107</b>	LED9WA19/ADV/830-G8	750	9W	3000K	80+	120V	10,000	E26	60W	5
<b>10282</b>	LED9WA19/ADV/830-G9	800	9W	3000K	80+	120V	15,000	E26	60W	5
<b>60405</b>	LED12WA19/ADV/827K-DIM-G7 2PK	1,050	12W	2700K	80+	120V	10,000	E26	75W	5
<b>60413</b>	LED12WA19/ADV/827K-G7 2PK	1,050	12W	2700K	80+	120V	10,000	E26	75W	5
<b>60406</b>	LED12WA19/ADV/830K-DIM-G7 2PK	1,050	12W	3000K	80+	120V	10,000	E26	75W	5
<b>60414</b>	LED12WA19/ADV/830K-G7 2PK	1,050	12W	3000K	80+	120V	10,000	E26	75W	5
<b>60407</b>	LED12WA19/ADV/840K-DIM-G7 2PK	1,050	12W	4000K	80+	120V	10,000	E26	75W	5
<b>60415</b>	LED12WA19/ADV/840K-G7 2PK	1,050	12W	4000K	80+	120V	10,000	E26	75W	5
<b>60408</b>	LED12WA19/ADV/850K-DIM-G7 2PK	1,050	12W	5000K	80+	120V	10,000	E26	75W	5
<b>60409</b>	LED16WA21/ADV/827K-DIM-G7 2PK	1,550	16W	2700K	80+	120V	10,000	E26	100W	7
<b>60417</b>	LED16WA21/ADV/827K-G7 2PK	1,550	16W	2700K	80+	120V	10,000	E26	100W	7
<b>60410</b>	LED16WA21/ADV/830K-DIM-G7 2PK	1,550	16W	3000K	80+	120V	10,000	E26	100W	7
<b>60418</b>	LED16WA21/ADV/830K-G7 2PK	1,550	16W	3000K	80+	120V	10,000	E26	100W	7
<b>60411</b>	LED16WA21/ADV/840K-DIM-G7 2PK	1,550	16W	4000K	80+	120V	10,000	E26	100W	7
<b>60419</b>	LED16WA21/ADV/840K-G7 2PK	1,550	16W	4000K	80+	120V	10,000	E26	100W	7
<b>60420</b>	LED16WA21/ADV/850K-G7 2PK	1,550	16W	5000K	80+	120V	10,000	E26	100W	7





## Filament Decorative Lamps

- Same vintage look and feel as incandescent filament lamps
- 80% more efficient and 20x longer life than incandescent
- Compatible with a range of leading edge TRIAC dimmers
- Suitable for use in damp locations/totally enclosed fixtures

### Filament Decorative

Order Code	Item	Lm	W	CCT	CRI	V	Life/Hrs L70	Base	Replaces Incan.	Photo #	ES
09858	LED2.5WB11E12/FIL/827-DIM-G7	200	3W	2700K	80+	120	15,000	E12	25W	1	★
09869	LED2.5WT10/FIL/827-DIM-G7	250	3W	2700K	80+	120	15,000	E26	25W	2	
09866	LED2.5WT6.5E17/FIL/827-DIM-G7	200	3W	2700K	80+	120	15,000	E17	20W	3	
09865	LED2WT6E12/FIL/827-DIM-G7	120	2W	2700K	80+	120	15,000	E12	15W	4	
09855	LED4WA15/FIL/827-DIM-G7	300	4W	2700K	80+	120	15,000	E26	25W	5	
09892	LED4WB11E12/FIL/827-DIM-G7	300	4W	2700K	80+	120	15,000	E12	40W	1	★
09860	LED4WBA11E12/FIL/827-DIM-G7	300	4W	2700K	80+	120	15,000	E12	40W	10	
09861	LED4WG16/FIL/827-DIM-G7	350	4W	2700K	80+	120	15,000	E26	40W	8	
09863	LED4WS14/FIL/822-DIM-G7	250	4W	2700K	80+	120	15,000	E26	25W	11	
09864	LED4WS14/FIL/827-DIM-G7	300	4W	2700K	80+	120	15,000	E26	40W	11	
09879	LED4WST19/FIL/822-DIM-G7	400	4W	2700K	80+	120	15,000	E26	40W	12	
09870	LED4WT10/FIL/827-DIM-G7	450	4W	2700K	80+	120	15,000	E26	40W	2	
09867	LED4WT6.5E17/FIL/827-DIM-G7	350	4W	2700K	80+	120	15,000	E17	25W	3	
09856	LED4.5WA15/FIL/827-DIM-G7	450	5W	2700K	80+	120	15,000	E26	40W	5	
09871	LED4.5WA19/FIL/822-DIM-G7	350	5W	2200K	80+	120	15,000	E26	25W	6	
09857	LED4.5WA19/FIL/SB/827-DIM-G7	400	5W	2700K	80+	120	15,000	E26	60W	7	
09859	LED4.5WB11E12/FIL/827-DIM-G7	500	5W	2700K	80+	120	15,000	E12	60W	1	
09862	LED4.5WG16/FIL/827-DIM-G7	500	5W	2700K	80+	120	15,000	E26	60W	8	
09875	LED4.5WG25/FIL/827-DIM-G7	470	5W	2700K	80+	120	15,000	E26	40W	9	
09868	LED4.5WT6.5E17/FIL/827-DIM-G7	450	5W	2700K	80+	120	15,000	E17	40W	3	
09878	LED5WB11E26/FIL/827-DIM-G7	500	5W	2700K	80+	120	15,000	E26	60W	13	
09877	LED7WA19/FIL/827-DIM-G7	800	7W	2700K	80+	120	15,000	E26	60W	6	★
09441	LED7WA19/FIL/SB/827K-DIM-G7	700	7W	2700K	80+	120	15,000	E26	60W	7	





## PL CFL Replacement Lamps

- Directly replaces PL compact fluorescent lamps
- Available in direct fit “plug and play” options or hybrid dual mode that also functions on line voltage
- Available in horizontal or vertical orientation
- Choice of 2700K, 3000K, 3500K and 4000K CCT
- Instant-on with no warmup, unlike compact fluorescent
- Shatter-resistant for reduced risk of injury and breakage
- Dimmable models available (ballast dependent)
- Environmentally friendly; contains no glass, lead or mercury

### PL Replacement

Order Code	Item	Lm	W	CCT	CRI	V	Life/Hrs L70	Base	Replaces CFL	Photo #	DLC
09530	LED7W2PH/GX23/827-G7	650	7W	2700K	80+	120-277V	50,000	GX23	13W	2	
09531	LED7W2PH/GX23/835-G7	650	7W	3500K	80+	120-277V	50,000	GX23	13W	2	
09532	LED7W2PH/GX23/840-G7	700	7W	4000K	80+	120-277V	50,000	GX23	13W	2	
09533	LED7W2PH/GX23/850-G7	700	7W	5000K	80+	120-277V	50,000	GX23	13W	2	
09332	LED9W2PH/827DR-G6	850	9W	2700K	80+	120-277V	50,000	G24d, GX24d	26W	3	
09250	LED9W2PH/830DR-G6	850	9W	3000K	80+	120-277V	50,000	G24d, GX24d	26W	3	
09251	LED9W2PH/835DR-G6	850	9W	3500K	80+	120-277V	50,000	G24d, GX24d	26W	3	
09252	LED9W2PH/840DR-G6	900	9W	4000K	80+	120-277V	50,000	G24d, GX24d	26W	3	
09253	LED9W2PV/830DR-G6	850	9W	3000K	80+	120-277V	50,000	G24d, GX24d	26W	4	
09254	LED9W2PV/835DR-G6	850	9W	3500K	80+	120-277V	50,000	G24d, GX24d	26W	4	
09255	LED9W2PV/840DR-G6	900	9W	4000K	80+	120-277V	50,000	G24d, GX24d	26W	4	
09938	LED9W4PH/827DR-G7	900	9W	2700K	80+	120-277V	50,000	G24q, GX24q	18W	5	✓
09901	LED9W4PH/830DR-G7	950	9W	3000K	80+	120-277V	50,000	G24q, GX24q	18W	5	✓
09902	LED9W4PH/835DR-G7	950	9W	3500K	80+	120-277V	50,000	G24q, GX24q	18W	5	✓
09903	LED9W4PH/840DR-G7	1,000	9W	4000K	80+	120-277V	50,000	G24q, GX24q	18W	5	✓
09333	LED9W4PV/827DR-G6	850	9W	2700K	80+	120-277V	50,000	G24q, GX24q	18W	7	
09939	LED9W4PV/827DR-G7	900	9W	2700K	80+	120-277V	50,000	G24q, GX24q	18W	7	✓
09940	LED9W4PV/830DR-G7	950	9W	3000K	80+	120-277V	50,000	G24q, GX24q	18W	7	✓
09925	LED9W4PV/835DR-G7	950	9W	3500K	80+	120-277V	50,000	G24q, GX24q	18W	7	✓
09926	LED9W4PV/840DR-G7	1,000	9W	4000K	80+	120-277V	50,000	G24q, GX24q	18W	7	✓



**PL Replacement** : Dual Mode

Order Code	Item	Lm	W	CCT	CRI	V	Life/Hrs L70	Base	Replaces Incan.	Photo #
10172	LED5W2P/G23/827DM-G7B	475	5W	2700K	80+	120-277	50,000	G23	13W	8
10173	LED5W2P/G23/830DM-G7B	475	5W	3000K	80+	120-277	50,000	G23	13W	8
10174	LED5W2P/G23/835DM-G7B	475	5W	3500K	80+	120-277	50,000	G23	13W	8
10180	LED5W2P/G23/840DM-G7B	475	5W	4000K	80+	120-277	50,000	G23	13W	8
09782	LED5W2PH/G23/835DM-G7B	500	5W	3500K	80+	120-277	50,000	G23	13W	8
09626	LED7W2PH/G23/835DM-G7	700	7W	3500K	80+	120-277	50,000	G23	18W	10
09627	LED7W2PH/GX23/835DM-G7	700	7W	3500K	80+	120-277	50,000	G23	18W	10
10176	LED7W2P/GX23/827DM-G7B	700	7W	2700K	80+	120-277	50,000	GX23	18W	9
10177	LED7W2P/GX23/830DM-G7B	700	7W	3000K	80+	120-277	50,000	GX23	18W	9
09904	LED7W2P/GX23/835DM-G7B	700	7W	3500K	80+	120-277	50,000	GX23	18W	9
10178	LED7W2P/GX23/840DM-G7B	700	7W	4000K	80+	120-277	50,000	GX23	18W	9
10163	LED12W2PH/GX23/827DM-G7	1,100	12W	2700K	80+	120-277	50,000	GX23	26W	9
10164	LED12W2PH/GX23/830DM-G7	1,100	12W	3000K	80+	120-277	50,000	GX23	26W	9
09629	LED12W2PH/GX23/835DM-G7	1,100	12W	3500K	80+	120-277	50,000	GX23	26W	9
10179	LED12W2PH/GX23/840DM-G7	1,100	12W	4000K	80+	120-277	50,000	GX23	26W	9
10166	LED12W4PH/G24Q/827DM-G7	1,100	12W	2700K	80+	120-277	50,000	G24Q	26W	10
10167	LED12W4PH/G24Q/830DM-G7	1,100	12W	3000K	80+	120-277	50,000	G24Q	26W	10
09630	LED12W4PH/G24Q/835DM-G7	1,100	12W	3500K	80+	120-277	50,000	G24Q	26W	10
10168	LED12W4PH/G24Q/840DM-G7	1,100	12W	4000K	80+	120-277	50,000	G24Q	26W	10
10169	LED12W4PV/G24Q/827DM-G7	1,100	12W	2700K	80+	120-277	50,000	G24Q	26W	11
10170	LED12W4PV/G24Q/830DM-G7	1,100	12W	3000K	80+	120-277	50,000	G24Q	26W	11
09631	LED12W4PV/G24Q/835DM-G7	1,100	12W	3500K	80+	120-277	50,000	G24Q	26W	11
10171	LED12W4PV/G24Q/840DM-G7	1,100	12W	4000K	80+	120-277	50,000	G24Q	26W	11







## PLL Replacement Lamps

- Solid state replacement for 2' 40W PLL compact fluorescent lamps with 2G11 base
- Frosted lens for uniform diffuse appearance
- Ultra-high performance LEDs deliver 100 lpw
- Lifetime exceeds 50,000 hrs
- Up to 50% instant energy savings
- Choice of 3000K, 3500K, 4000K, and 5000K CCT
- Instant-on with no warm up, unlike fluorescents

### PLL Replacement

Order Code	Item	Lm	W	CCT	CRI	V	Life/Hrs L70	Base	Beam	Photo #
<b>60461</b>	LED23W/PLL/830-G7DR	2,600	23W	3000K	82+	120-277	50,000	2G11	120°	1
<b>60462</b>	LED23W/PLL/835-G7DR	2,600	23W	3500K	82+	120-277	50,000	2G11	120°	1
<b>60463</b>	LED23W/PLL/840-G7DR	2,800	23W	4000K	82+	120-277	50,000	2G11	120°	1
<b>60464</b>	LED23W/PLL/850-G7DR	2,800	23W	5000K	82+	120-277	50,000	2G11	120°	1





## BR Replacement Lamps

- Direct replacement for incandescent BR lamps
- 80% more efficient and 20x longer life than incandescent
- Smooth aluminum body with ANSI standard form factor
- Acceptable for ICAT rated downlights

### BR Replacement

Order Code	Item	Lm	W	CCT	CRI	V	Life/Hrs L70	Base	Replaces Incan.	Photo #	ES
10087	LED7WBR20/827-DIM-G8	550	7W	2700K	80+	120	25,000	E26	50W	1	★
10005	LED7WBR20/830-DIM-G8	550	7W	3000K	80+	120	25,000	E26	50W	1	★
10006	LED7WBR20/840-DIM-G8	550	7W	4000K	80+	120	25,000	E26	50W	1	
10375	LED8WBR30/827-DIM-G9	650	8W	2700K	80+	120	25,000	E26	75W	2	
10376	LED8WBR30/830-DIM-G9	650	8W	3000K	80+	120	25,000	E26	75W	2	
10377	LED8WBR30/840-DIM-G9	650	8W	4000K	80+	120	25,000	E26	75W	2	
09999	LED8WBR30/827-DIM-G8	650	8W	2700K	80+	120	25,000	E26	75W	2	★
10000	LED8WBR30/830-DIM-G8	650	8W	3000K	80+	120	25,000	E26	75W	2	★
10001	LED8WBR30/840-DIM-G8	650	8W	4000K	80+	120	25,000	E26	75W	2	★
10375	LED8WBR30/827-DIM-G9	650	8W	2700K	80+	120	25,000	E26	75W	2	
10376	LED8WBR30/830-DIM-G9	650	8W	3000K	80+	120	25,000	E26	75W	2	
10377	LED8WBR30/840-DIM-G9	650	8W	4000K	80+	120	25,000	E26	75W	2	
10002	LED11WBR30/827-DIM-G8	850	11W	2700K	80+	120	25,000	E26	75W	2	★
10003	LED11WBR30/830-DIM-G8	850	11W	3000K	80+	120	25,000	E26	75W	2	★
10004	LED11WBR30/840-DIM-G8	850	11W	4000K	80+	120	25,000	E26	75W	2	★
10086	LED11WBR30/850-DIM-G8	650	11W	5000K	80+	120	25,000	E26	75W	2	★
10084	LED12WBR40/827-DIM-G8	1,050	12W	2700K	80+	120	25,000	E26	80W	3	
09998	LED12WBR40/830-DIM-G8	1,050	12W	3000K	80+	120	25,000	E26	80W	3	★
10085	LED12WBR40/840-DIM-G8	1,050	12W	4000K	80+	120	25,000	E26	80W	3	
10010	LED17WBR40/827-DIM-G8	1,400	17W	2700K	80+	120	25,000	E26	100W	3	
09996	LED17WBR40/830-DIM-G8	1,400	17W	3000K	80+	120	25,000	E26	100W	3	★
09997	LED17WBR40/840-DIM-G8	1,400	17W	4000K	80+	120	25,000	E26	100W	3	★





## PAR Replacement Lamps

- Direct replacement for halogen PARs
- Compatible with a wide array of dimmers
- 25,000 hour rated life for ENERGY STAR® Approved lamps
- 50,000 hour design life
- Up to 80% electricity savings vs. halogen
- Choice of 2700K, 3000K and 4000K CCT
- Environmentally friendly: contains no glass, mercury, or lead

### PAR16 Replacement

Order Code	Item	Lm	W	CCT	CRI	V	Life/Hrs L70	Base	Replaces Incan.	Photo #	ES
09041	LED7WPAR16/FL/827K-DIM-G5	490	7W	2700K	80+	120	25,000	E26	50W	1	★
09042	LED7WPAR16/FL/830K-DIM-G5	490	7W	3000K	80+	120	25,000	E26	50W	1	★
09043	LED7WPAR16/FL/840K-DIM-G5	490	7W	4000K	80+	120	25,000	E26	50W	1	★
09038	LED7WPAR16/NFL/827K-DIM-G5	490	7W	2700K	80+	120	25,000	E26	50W	1	★
09039	LED7WPAR16/NFL/830K-DIM-G5	490	7W	3000K	80+	120	25,000	E26	50W	1	★
09040	LED7WPAR16/NFL/840K-DIM-G5	490	7W	4000K	80+	120	25,000	E26	50W	1	★

### PAR20 Replacement

Order Code	Item	Lm	W	CCT	CRI	V	Life/Hrs L70	Base	Replaces Incan.	Photo #	ES
09970	LED7WPAR20/FL/827-DIM-G8	500	7W	2700K	80+	120	25,000	E26	50W	2	★
09971	LED7WPAR20/FL/830-DIM-G8	500	7W	3000K	80+	120	25,000	E26	50W	2	★
09984	LED7WPAR20/FL/840-DIM-G8	500	7W	4000K	80+	120	25,000	E26	50W	2	★
09985	LED7WPAR20/NFL/827-DIM-G8	500	7W	2700K	80+	120	25,000	E26	50W	2	
09986	LED7WPAR20/NFL/830-DIM-G8	500	7W	3000K	80+	120	25,000	E26	50W	2	★
09972	LED7WPAR20/NFL/840-DIM-G8	500	7W	4000K	80+	120	25,000	E26	50W	2	★
90019	LED7WPAR20/NFL/840K-DIM-G4A	500	7W	4000K	80+	120	25,000	E26	55W	2	



## PAR30 Replacement

Order Code	Item	Lm	W	CCT	CRI	V	Life/Hrs L70	Base	Replaces Incan.	Photo #	ES
09993	LED11WPAR30/FL/827-DIM-G8	850	11W	2700K	80+	120	25,000	E26	75W	3	★
09155	LED11WPAR30/FL/827K-DIM-G6	850	11W	2700K	80+	120	25,000	E26	75W	3	★
10070	LED11WPAR30/FL/830-DIM-G8	850	11W	3000K	80+	120	25,000	E26	75W	3	★
10071	LED11WPAR30/FL/840-DIM-G8	850	11W	4000K	80+	120	25,000	E26	75W	3	
09994	LED11WPAR30/FL/850-DIM-G8	850	11W	5000K	80+	120	25,000	E26	75W	3	
10072	LED11WPAR30/NFL/827-DIM-G8	850	11W	2700K	80+	120	25,000	E26	75W	3	
10073	LED11WPAR30/NFL/830-DIM-G8	850	11W	3000K	80+	120	25,000	E26	75W	3	
10074	LED11WPAR30/NFL/840-DIM-G8	850	11W	4000K	80+	120	25,000	E26	75W	3	
10075	LED11WPAR30S/FL/827-DIM-G8	850	11W	2700K	80+	120	25,000	E26	75W	4	
10076	LED11WPAR30S/FL/830-DIM-G8	850	11W	3000K	80+	120	25,000	E26	75W	4	
10077	LED11WPAR30S/FL/840-DIM-G8	850	11W	4000K	80+	120	25,000	E26	75W	4	
10078	LED11WPAR30S/NFL/827-DIM-G8	850	11W	2700K	80+	120	25,000	E26	75W	4	
10079	LED11WPAR30S/NFL/830-DIM-G8	850	11W	3000K	80+	120	25,000	E26	75W	4	
09476	LED12WPAR30S/FL/827-DIM-G7	950	12W	2700K	80+	120	25,000	E26	75W	4	★
09479	LED12WPAR30S/NFL/827-DIM-G7	950	12W	2700K	80+	120	25,000	E26	75W	4	★
08558	LED12WPAR30S/NFL/840-DIM-G4A	850	12W	4000K	80+	120	25,000	E26	75W	4	

## PAR38 Replacement

Order Code	Item	Lm	W	CCT	CRI	V	Life/Hrs L70	Base	Replaces Incan.	Photo #	ES
09161	LED13WPAR38/FL/827K-DIM-G6	1,050	13W	2700K	80+	120	25,000	E26	100W	5	★
09162	LED13WPAR38/FL/830K-DIM-G6	1,050	13W	3000K	80+	120	25,000	E26	100W	5	★
09163	LED13WPAR38/FL/840K-DIM-G6	1,050	13W	4000K	80+	120	25,000	E26	100W	5	★
09165	LED13WPAR38/NFL/830K-DIM-G6	1,050	13W	3000K	80+	120	25,000	E26	100W	5	
10069	LED15WPAR38/FL/827-DIM-G8	1,250	15W	2700K	80+	120	25,000	E26	120W	5	
09990	LED15WPAR38/FL/830-DIM-G8	1,250	15W	3000K	80+	120	25,000	E26	120W	5	★
09991	LED15WPAR38/FL/840-DIM-G8	1,250	15W	4000K	80+	120	25,000	E26	120W	5	
09992	LED15WPAR38/FL/850-DIM-G8	1,250	15W	5000K	80+	120	25,000	E26	120W	5	
10066	LED15WPAR38/NFL/840-DIM-G8	1,250	15W	4000K	80+	120	25,000	E26	120W	5	
09170	LED20WPAR38/FL/827K-DIM-G6	1,700	20W	2700K	80+	120	25,000	E26	150W	6	★
09171	LED20WPAR38/FL/830K-DIM-G6	1,700	20W	3000K	80+	120	25,000	E26	150W	6	★
09172	LED20WPAR38/FL/840K-DIM-G6	1,700	20W	4000K	80+	120	25,000	E26	150W	6	★





## MR Replacement Lamps

- Direct replacement for halogen miniature reflector lamps
- 25,000 hour rated life lasting 20x longer than halogen incandescent
- Choice of 2700K, 3000K and 4000K CCT
- Available in 2 beam distributions: 25° Narrow Flood & 40° Flood
- Shatter-resistant for reduced risk of injury or breakage
- Contains no lead or mercury; RoHS compliant

### MR Replacement

Order Code	Item	Lm	W	CCT	CRI	V	Life/Hrs L70	Base	Replaces Incan.	Photo #	ES
10067	LED7WGU10/FL/827-DIM-G8	500	7W	2700K	80+	120	25,000	GU10	50W	1	
10011	LED7WGU10/FL/830-DIM-G8	500	7W	3000K	80+	120	25,000	GU10	50W	1	★
10081	LED7WGU10/FL/840-DIM-G8	500	7W	4000K	80+	120	25,000	GU10	50W	1	
09988	LED7WGU10/NFL/827-DIM-G8	500	7W	2700K	80+	120	25,000	GU10	50W	1	
10013	LED7WGU10/NFL/830-DIM-G8	500	7W	3000K	80+	120	25,000	GU10	50W	1	★
09989	LED7WGU10/NFL/840-DIM-G8	500	7W	4000K	80+	120	25,000	GU10	50W	1	★
09493	LED7WMR16/FL/827-DIM-G7	500	7W	2700K	80+	12	25,000	GU5.3	50W	2	★
09494	LED7WMR16/FL/830-DIM-G7	500	7W	3000K	80+	12	25,000	GU5.3	50W	2	★
09495	LED7WMR16/FL/840-DIM-G7	500	7W	4000K	80+	12	25,000	GU5.3	50W	2	★
09543	LED7WMR16/NFL/827-DIM-G7	500	7W	2700K	80+	12	25,000	GU5.3	50W	2	★
09544	LED7WMR16/NFL/830-DIM-G7	500	7W	3000K	80+	12	25,000	GU5.3	50W	2	★
09545	LED7WMR16/NFL/840-DIM-G7	500	7W	4000K	80+	12	25,000	GU5.3	50W	2	★

### Elevator Lights

Order Code	Item	Lm	W	CCT	CRI	V	Life/Hrs L70	Base	Replaces Incan.	Photo #
08896	LED3W1383/30/830-G5	125	3W	3000K	80+	12	20,000	BA15s	1383	3
08899	LED3W1383/30/840-G5	125	3W	4000K	75+	12	20,000	BA15s	1383	3
08895	LED3WGGBF/30/830-G5	125	3W	3000K	80+	12	20,000	BA15d	GBF	4
08900	LED3WGGBF/30/840-G5	125	3W	4000K	75+	12	20,000	BA15d	GBF	4





## Decorative Replacement Lamps

- Direct replacement for incandescent globe and bullet lamps
- 15,000 hour rated life
- 50,000 hour design life
- Ideal for wall sconces and ceiling fans
- Available in 2700K, 3000K and 4000K CCT
- Lasts 10x longer than incandescent
- Instant-on with no warm up, unlike CFLs
- Not for use in enclosed fixtures

### Decorative Replacement

Order Code	Item	Lm	W	CCT	CRI	V	Life/Hrs L70	Base	Replaces Incan.	Photo #	ES
10088	LED5WB11/E26/827-DIM-G8	350	5W	2700K	80+	120	25,000	E26	40W	1	★
10089	LED5WB11/E26/830-DIM-G8	325	5W	3000K	80+	120	25,000	E26	40W	1	
10007	LED5WB11/E12/827-DIM-G8	325	5W	2700K	80+	120	25,000	E12	40W	2	★
10008	LED5WB11/E12/830-DIM-G8	325	5W	3000K	80+	120	25,000	E12	40W	2	★
10082	LED6WG25/827-DIM-G8	450	6W	2700K	80+	120	25,000	E26	40W	3	
10083	LED6WG25/830-DIM-G8	450	6W	3000K	80+	120	25,000	E26	40W	3	★
09995	LED6WG25/840-DIM-G8	450	6W	4000K	80+	120	25,000	E26	40W	3	★





## G4 & G9 Replacement Lamps

- Direct replacement for halogen incandescent G4 & G9 lamps
- Consumes 75% less energy and lasts 25x longer than incandescent bulbs
- 25,000 hour rated life
- Choice of 3000K, 4000K, and 5000K CCT
- 200° multi-directional beam angle
- Integrated driver

### G4 & G9 Replacement

Order Code	Item	Lm	W	CCT	CRI	V	Life/Hrs L70	Base	Replaces Incan.	Photo #
<b>08606</b>	LED2WG4/840K-G4	200	3W	4000K	80+	12	25,000	G4	10W	1
<b>08607</b>	LED2WG4/850K-G4	200	3W	5000K	80+	12	25,000	G4	10W	1






## Outdoor Fixtures

- Cost-effective, solid-state LED solutions for site, area, high mast, highbay, and flood lighting
- IP65 Rated
- Wet location rated
- Instant-on with no warmup
- 5 year system warranty
- Long 50K+ hour life reduces maintenance costs
- Flexible mounting options for a variety of applications

### VERT : Site Lighting Platform

Order Code	Item	Lm	W	CCT	CRI	V	Life/Hrs L70	Dim	Optics	Photo #	DLC Premium
10137	VRT1-130/C5/740-U-D-T3-BZ	13,000	100W	4000K	70+	100-277V	50,000	0-10V	Type 3	1	✓✓
10150	VRT1-130/C5/740-U-D-T5-BZ	13,000	100W	4000K	70+	100-277V	50,000	0-10V	Type 5	1	
10138	VRT1-130/C5/750-U-D-T3-BZ	13,000	100W	5000K	70+	100-277V	50,000	0-10V	Type 3	1	✓✓
10151	VRT1-130/C5/750-U-D-T5-BZ	13,000	100W	5000K	70+	100-277V	50,000	0-10V	Type 5	1	
10139	VRT1-195/C5/740-U-D-T3-BZ	19,500	150W	4000K	70+	100-277V	50,000	0-10V	Type 3	1	✓✓
10152	VRT1-195/C5/740-U-D-T5-BZ	19,500	150W	4000K	70+	100-277V	50,000	0-10V	Type 5	1	✓✓
10141	VRT1-195/C5/740-V-D-T3-BZ	19,500	150W	4000K	70+	200-480V	50,000	0-10V	Type 3	1	✓✓
10154	VRT1-195/C5/740-V-D-T5-BZ	19,500	150W	4000K	70+	200-480V	50,000	0-10V	Type 5	1	✓✓
10140	VRT1-195/C5/750-U-D-T3-BZ	19,500	150W	5000K	70+	100-277V	50,000	0-10V	Type 3	1	✓✓
10153	VRT1-195/C5/750-U-D-T5-BZ	19,500	150W	5000K	70+	100-277V	50,000	0-10V	Type 5	1	✓✓
10142	VRT1-195/C5/750-V-D-T3-BZ	19,500	150W	5000K	70+	200-480V	50,000	0-10V	Type 3	1	✓✓
10155	VRT1-195/C5/750-V-D-T5-BZ	19,500	150W	5000K	70+	200-480V	50,000	0-10V	Type 5	1	✓✓
10143	VRT2-240/C5/740-U-D-T3-BZ	24,000	185W	4000K	70+	100-277V	50,000	0-10V	Type 3	2	✓✓
10156	VRT2-240/C5/740-U-D-T5-BZ	24,000	185W	4000K	70+	100-277V	50,000	0-10V	Type 5	2	✓✓
10144	VRT2-240/C5/750-U-D-T3-BZ	24,000	185W	5000K	70+	100-277V	50,000	0-10V	Type 3	2	✓✓
10157	VRT2-240/C5/750-U-D-T5-BZ	24,000	185W	5000K	70+	100-277V	50,000	0-10V	Type 5	2	✓✓
10145	VRT2-380/C5/740-U-D-T3-BZ	38,000	300W	4000K	70+	100-277V	50,000	0-10V	Type 3	2	✓✓
10158	VRT2-380/C5/740-U-D-T5-BZ	38,000	300W	4000K	70+	100-277V	50,000	0-10V	Type 5	2	✓✓
10148	VRT2-380/C5/740-V-D-T3-BZ	38,000	300W	4000K	70+	200-480V	50,000	0-10V	Type 3	2	✓✓
10160	VRT2-380/C5/740-V-D-T5-BZ	38,000	300W	4000K	70+	200-480V	50,000	0-10V	Type 5	2	✓✓
10147	VRT2-380/C5/750-U-D-T3-BZ	38,000	300W	5000K	70+	100-277V	50,000	0-10V	Type 3	2	✓✓
10159	VRT2-380/C5/750-U-D-T5-BZ	38,000	300W	5000K	70+	100-277V	50,000	0-10V	Type 5	2	✓✓

Continued on next page >>>





**VERT : Site Lighting Platform**

Order Code	Item	Lm	W	CCT	CRI	V	Life/Hrs L70	Dim	Optics	Photo #	DLC Premium
10149	VRT2-380/C5/750-V-D-T3-BZ	38,000	300W	5000K	70+	200-480V	50,000	0-10V	Type 3	2	✓✓
10161	VRT2-380/C5/750-V-D-T5-BZ	38,000	300W	5000K	70+	200-480V	50,000	0-10V	Type 5	2	✓✓

**VERT : Mounting Options (Must be ordered with fixture)**

Order Code	Item	Description
10162	VRT-S-BZ	Slipfitter Mount for VERT, 2 3/8", Bronze
10135	VRT-D-BZ	Direct Mount for VERT, Bronze

Order Code	Item	Description
10134	VRT-Y-BZ	Yoke Mount for VERT, Bronze

**SIGNAL : Floodlight & Highbay**

Order Code	Item	Lm	W	CCT	CRI	V	Life/Hrs L70	Dim	Photo #
10290	SIG-720/G0/740-U-D-G-BK	72,000	450W	4000K	70+	120-277V	50,000	0-10V	3
10294	SIG-720/G0/740-V-D-G-BK	72,000	450W	4000K	70+	277-480V	50,000	0-10V	3
10291	SIG-720/G0/750-U-D-G-BK	72,000	450W	5000K	70+	120-277V	50,000	0-10V	3
10295	SIG-720/G0/750-V-D-G-BK	72,000	450W	5000K	70+	277-480V	50,000	0-10V	3
10292	SIG-960/G0/740-U-D-G-BK	96,000	600W	4000K	70+	120-277V	50,000	0-10V	3
10296	SIG-960/G0/740-V-D-G-BK	96,000	600W	4000K	70+	277-480V	50,000	0-10V	3
10293	SIG-960/G0/750-U-D-G-BK	96,000	600W	5000K	70+	120-277V	50,000	0-10V	3
10297	SIG-960/G0/750-V-D-G-BK	96,000	600W	5000K	70+	277-480V	50,000	0-10V	3

**SIGNAL : Accessories**

Order Code	Item	Description
10188	SIG-LENS-PC30D	Signal Lens, 30°
10189	SIG-LENS-PC60D	Signal Lens, 60°
10190	SIG-REFLECTOR-AL90D	Signal Refelctor, Aluminum, 90°
10298	SIG-S-BK	Signal Slipfitter for up to 2 3/8 Pipe

Order Code	Item	Description
10187	SIG-SMK-BK	Signal Surface Mount Kit, Black
10185	SIG-VISOR-BK	Signal Visor, Black
10186	SIG-Y-BK	Signal Yoke Mounting Bracket, Black

**FLJ : Flood Light Mini**

Order Code	Item	Lm	W	CCT	CRI	V	Life/Hrs L70	Mount	Replaces HID	Photo #	DLC
09619	FLJ-1C-30K-K-U	1,350	12W	3000K	80+	120-277V	50,000	Knuckle	150W	4	✓
09618	FLJ-1C-30K-Y-U	1,350	12W	3000K	80+	120-277V	50,000	Yoke	150W	5	✓
09612	FLJ-1C-50K-K-U	1,350	12W	5000K	80+	120-277V	50,000	Knuckle	150W	4	✓
09611	FLJ-1C-50K-Y-U	1,350	12W	5000K	80+	120-277V	50,000	Yoke	150W	5	✓
09614	FLJ-3C-30K-K-U	3,200	30W	3000K	80+	120-277V	50,000	Knuckle	300W	6	✓
09613	FLJ-3C-30K-Y-U	3,200	30W	3000K	80+	120-277V	50,000	Yoke	300W	7	✓
09623	FLJ-3C-50K-K-U	3,200	30W	5000K	80+	120-277V	50,000	Knuckle	300W	6	✓
09615	FLJ-3C-50K-Y-U	3,200	30W	5000K	80+	120-277V	50,000	Yoke	300W	7	✓
09621	FLJ-5C-30K-K-U	5,400	50W	3000K	80+	120-277V	50,000	Knuckle	300W	8	✓
09620	FLJ-5C-30K-Y-U	5,400	50W	3000K	80+	120-277V	50,000	Yoke	300W	9	✓
09617	FLJ-5C-50K-K-U	5,400	50W	5000K	80+	120-277V	50,000	Knuckle	300W	8	✓
09616	FLJ-5C-50K-Y-U	5,400	50W	5000K	80+	120-277V	50,000	Yoke	300W	9	✓

Continued on next page >>>



**FLJ** : Flood Light Mini

Order Code	Item	Lm	W	CCT	CRI	V	Life/Hrs L70	Mount	Replaces HID	Photo #	DLC
10304	FLJ-108/D5/740-U-D-S-BZ	10,800	80W	4000K	70+	100-277V	50,000	Slipfitter	350W	10	✓
10305	FLJ-108/D5/750-U-D-S-BZ	10,800	80W	5000K	70+	100-277V	50,000	Slipfitter	350W	10	✓
10306	FLJ-130/D0/740-U-D-S-BZ	13,000	100W	4000K	70+	100-277V	50,000	Slipfitter	350W	10	✓
10307	FLJ-130/D0/740-V-D-S-BZ	13,000	100W	4000K	70+	277-480V	50,000	Slipfitter	350W	10	✓
10308	FLJ-130/D0/750-U-D-S-BZ	13,000	100W	5000K	70+	100-277V	50,000	Slipfitter	350W	10	✓
10309	FLJ-130/D0/750-V-D-S-BZ	13,000	100W	5000K	70+	277-480V	50,000	Slipfitter	350W	10	✓
10310	FLJ-165/B0/840-U-D-S-BZ	16,500	150W	4000K	70+	100-277V	50,000	Slipfitter	400W	11	✓
10311	FLJ-165/B0/840-V-D-S-BZ	16,500	150W	4000K	70+	277-480V	50,000	Slipfitter	400W	11	✓
10312	FLJ-165/B0/850-U-D-S-BZ	16,500	150W	5000K	70+	100-277V	50,000	Slipfitter	400W	11	✓
10313	FLJ-165/B0/850-V-D-S-BZ	16,500	150W	5000K	70+	277-480V	50,000	Slipfitter	400W	11	✓

**FLJ** : Accessories

Order Code	Item	Description
10314	FLJ-YA-BZ	Mounting adaptor





## High Bay Fixtures

- Cost-effective, solid-state solutions for highbay and lowbay applications
- Replaces high-watt HID fixtures and/or multi-lamp fluorescent luminaires
- Available in round and linear configurations
- Range of available accessories to customize fixtures to individual needs
- 5 year system warranty

### BAY : Round Bay Light

Order Code	Item	Lm	W	CCT	CRI	V	Life/Hrs L70	Dim	Replaces Fluor.	Photo #	DLC
09796	BAY-3C-40K-U	12,500	100W	4000K	80+	100-277V	50,000	1-10V	150-175W	1	✓
09797	BAY-3C-40K-V	12,500	100W	4000K	80+	200-480V	50,000	1-10V	150-175W	1	✓
09582	BAY-3C-50K-U	12,500	100W	5000K	80+	100-277V	50,000	1-10V	150-175W	1	✓
09588	BAY-3C-50K-V	12,500	100W	5000K	80+	200-480V	50,000	1-10V	150-175W	1	✓
09798	BAY-4C-40K-U	18,750	150W	4000K	80+	100-277V	50,000	1-10V	250-320W	1	✓
09799	BAY-4C-40K-V	18,750	150W	4000K	80+	200-480V	50,000	1-10V	250-320W	1	✓
09583	BAY-4C-50K-U	18,750	150W	5000K	80+	100-277V	50,000	1-10V	250-320W	1	✓
09589	BAY-4C-50K-V	18,750	150W	5000K	80+	200-480V	50,000	1-10V	250-320W	1	✓
09800	BAY-5C-40K-U	25,000	200W	4000K	80+	100-277V	50,000	1-10V	320-400W	1	✓
09801	BAY-5C-40K-V	25,000	200W	4000K	80+	200-480V	50,000	1-10V	320-400W	1	✓
09584	BAY-5C-50K-U	25,000	200W	5000K	80+	100-277V	50,000	1-10V	320-400W	1	✓
09590	BAY-5C-50K-V	25,000	200W	5000K	80+	200-480V	50,000	1-10V	320-400W	1	✓

### BAY : Accessories

Order Code	Item	Description
09914	BAY-REFLECTOR-CV16	16" Cloudveil™ Reflector
09915	BAY-REFLECTOR-CV22	22" Cloudveil™ Reflector
09585	BAY-REFLECTOR-BT-AL-60D	60° Aluminum Reflector
09586	BAY-REFLECTOR-BT-AL-90D	90° Aluminum Reflector
09587	BAY-REFLECTOR-BT-PC-70D	70° Polycarbonate Reflector
10387	BAY-REFLECTOR-AC16	Light Reflector Clear Acrylic
09913	BAY-WG-GL	Wireguard, Glass

Order Code	Item	Description
09912	BAY-WG-AL	Wireguard, Aluminum Reflector
09911	BAY-WG-PC	Wireguard, PC Reflector
09910	BAY-SEN-1A-KIT	Occupancy/Photocontrol Kit, Remote Controllable
10382	BAY-CCL-16	16" Clear Conic Lens Acrylic
10384	BAY-CCL-22	22" Clear Conic Lens Acrylic
10383	BAY-CDL-16	16" Clear Drop Lens Acrylic
10385	BAY-CDL-22	22" Clear Drop Lens Acrylic
10386	BAY-CWB-16	16" Clear Wide Bay Lens Acrylic
10380	BAY-BAND-16	Stainless Steel Clamp Band, 16" Reflectors
10381	BAY-BAND-22	Stainless Steel Clamp Band, 22" Reflectors
10378	BAY-PA-1/2NPS-W	Pipe Adaptor 1/2" NPS White
10379	BAY-PA-3/4NPS-W	Pipe Adaptor 3/4" NPS White



## LLH : Linear Highbay

Order Code	Item	Lm	W	CCT	CRI	V	Life/Hrs L70	Dim	Replaces Fluor.	Photo #	DLC Premium
09538	LLH-1C-50K-U	14,410	107W	5000K	80+	120-277V	50,000	0-10V	HBF 6x T8/4x T5	2	✓✓
09703	LLH-1C-40K-U	14,300	110W	4000K	80+	120-277V	50,000	0-10V	HBF 6x T8/4x T5	2	✓✓
09793	LLH-1C-40K-V	14,300	110W	4000K	80+	347V	50,000	0-10V	HBF 6x T8/4x T5	2	
09571	LLH-1C-50K-U-1S	14,410	110W	5000K	80+	120-277V	50,000	0-10V	HBF 6x T8/4x T5	2	
09741	LLH-1C-50K-V	14,300	110W	5000K	80+	347V	50,000	0-10V	HBF 6x T8/4x T5	2	✓✓
09539	LLH-2C-50K-U	21,222	160W	5000K	80+	120-277V	50,000	0-10V	HBF 8x T8/6x T5 HO	2	✓✓
09771	LLH-2C-40K-U	21,060	162W	4000K	80+	120-277V	50,000	0-10V	HBF 8x T8/6x T5 HO	2	✓✓
09794	LLH-2C-40K-V	21,060	162W	4000K	80+	347V	50,000	0-10V	HBF 8x T8/6x T5 HO	2	
09572	LLH-2C-50K-U-1S	21,222	162W	5000K	80+	120-277V	50,000	0-10V	HBF 8x T8/6x T5 HO	2	
09742	LLH-2C-50K-V	21,060	162W	5000K	80+	347V	50,000	0-10V	HBF 8x T8/6x T5 HO	2	✓✓
09540	LLH-3C-50K-U	29,213	214W	5000K	80+	120-277V	50,000	0-10V	8x T5 HO	3	✓✓
09772	LLH-3C-40K-U	28,990	223W	4000K	80+	120-277V	50,000	0-10V	8x T5 HO	3	✓✓
09795	LLH-3C-40K-V	28,990	223W	4000K	80+	347-480V	50,000	0-10V	8x T5 HO	3	
09573	LLH-3C-50K-U-1S	29,213	223W	5000K	80+	120-277V	50,000	0-10V	8x T5 HO	3	
09591	LLH-3C-50K-V	28,990	223W	5000K	80+	347-480V	50,000	0-10V	8x T5 HO	3	✓✓
09773	LLH-4C-40K-U	34,450	265W	4000K	80+	120-277V	50,000	0-10V	8x T5 HO	3	✓✓
09541	LLH-4C-50K-U	34,715	265W	5000K	80+	120-277V	50,000	0-10V	8x T5 HO	3	✓✓
10265	LLH-5C-40K-V	42,000	321W	4000K	80+	347-480V	50,000	0-10V	8x T5 HO	3	
09542	LLH-5C-50K-U	41,920	314W	5000K	80+	120-277V	50,000	0-10V	8x T5 HO	3	✓✓
09592	LLH-5C-50K-V	41,920	320W	5000K	80+	347-480V	50,000	0-10V	8x T5 HO	3	✓✓
09774	LLH-5C-40K-U	41,920	321W	4000K	80+	120-277V	50,000	0-10V	8x T5 HO	3	✓✓

## LLH : Accessories

Order Code	Item	Description
09850	FHSCP-UNV-10.7WL	10.7W Emergency Battery Backup
09852	FHSCP-UNV-13.7WL	13.7W Emergency Battery Backup
09854	FHSCP-UNV-17WL	17W Emergency Battery Backup
09849	FHSCP-UNV-5WL	5W Emergency Battery Backup
09851	FHSCP-UNV-7.8WL	7.8W Emergency Battery Backup
09226	LLH-CHAIN	Mounting Chain for LLH, 1.05 meters (1 pair)
09336	LLH-CL-2x1	Clear Lens for LLH-1C-xxK-U
09337	LLH-CL-2x1.5	Clear Lens for LLH-2C-xxK-U
09338	LLH-CL-4x1	Clear Lens for LLH-3C-xxK-U
09700	LLH-CL-4x1.5	Replacement Clear Lens for LLH-4C-xxK-U, LLH-5C-xxK-U
09339	LLH-FL-2x1	Replacement Frosted Lens for LLH-1C-xxK-U
09340	LLH-FL-2x1.5	Replacement Frosted Lens for LLH-2C-xxK-U
09341	LLH-FL-4x1	Replacement Frosted Lens for LLH-3C-xxK-U

Order Code	Item	Description
09701	LLH-FL-4x1.5	Replacement Frosted Lens for LLH-4C-xxK-U, LLH-5C-xxK-U
09227	LLH-PENDANT BOX	Pendant Box for LLH, 3/4" NPT
09818	LLH-SMK-1	Surface Mount Kit, 12.6"
09819	LLH-SMK-2	Surface Mount Kit, 17.3"
09230	LLH-V HOOK-1	V-Hook (1 pair) for LLH-1C-xxK-U, LLH-3C-xxK-U
09229	LLH-V HOOK-1.5	V-Hook (1 pair) for LLH-2C-xxK-U, LLH-4C-xxK-U, LLH-5C-xxK-U
09222	LLH-WG-2x1	Wireguard for LLH-1C-xxK-U
09223	LLH-WG-2x1.5	Wireguard for LLH-2C-xxK-U
09224	LLH-WG-4x1	Wireguard for LLH-3C-xxK-U
09702	LLH-WG-4x1.5	Wireguard for LLH-4C-xxK-U, LLH-5C-xxK-U
09906	LLH-PENDANT BOX-347/480	Pendant Box for 347/480V LLH, 3/4" NPT
09890	SEN-3A-KO	Sensor, PIR OCC/PC
09908	SEN-S1A-KO	Sensor, OCC/PC/RC, IP65, 1/2" Knock Out Mount, Remote Controllable





## Linear Fixtures

- Cost-effective, energy-efficient replacements for fluorescent linear fixtures
- Durable and stylish construction
- Available in 4000K and 5000K color temperature
- Dimmable
- 5 year system warranty

### LLW : Linear Wrap

Order Code	Item	Size	Lm	W	CCT	CRI	V	Life/Hrs L70	Dim	Photo #	DLC Premium
<b>09704</b>	LLW-4CP-40K-U	4'	4,420	34W	4000K	80+	120-277	50,000	0-10V	1	✓✓
<b>09705</b>	LLW-5CP-40K-U	4'	5,200	40W	4000K	80+	120-277	50,000	0-10V	1	✓✓

### LLW : Accessories

Order Code	Item	Description
<b>09849</b>	FHSCP-UNV-5WL	5W Emergency Battery Backup
<b>09851</b>	FHSCP-UNV-7.8WL	7.8W Emergency Battery Backup
<b>09850</b>	FHSCP-UNV-10.7WL	10.7W Emergency Battery Backup

Order Code	Item	Description
<b>09852</b>	FHSCP-UNV-13.7WL	13.7W Emergency Battery Backup
<b>09854</b>	FHSCP-UNV-17WL	17W Emergency Battery Backup

### STR : Linear Strip

Order Code	Item	Size	Lm	W	CCT	CRI	V	Life/Hrs L70	Dim	Photo #	DLC Premium
<b>09534</b>	STR-2C-40K-U	4'	3,013	23W	4000K	80+	120-277	50,000	0-10V	2	✓✓
<b>09820</b>	STR-2C-50K-U	4'	3,013	23W	5000K	80+	120-277	50,000	0-10V	2	✓✓
<b>09535</b>	STR-3C-40K-U	4'	4,224	32W	4000K	80+	120-277	50,000	0-10V	2	✓✓
<b>09821</b>	STR-3C-50K-U	4'	4,224	32W	5000K	80+	120-277	50,000	0-10V	2	✓✓
<b>09536</b>	STR-4C-40K-U	4'	6,026	46W	4000K	80+	120-277	50,000	0-10V	2	✓✓
<b>09822</b>	STR-4C-50K-U	4'	6,026	46W	5000K	80+	120-277	50,000	0-10V	2	✓✓
<b>10351</b>	STR8-60/DO/840-U-D	8'	6,000	46W	4000K	80+	120-277V	50,000	0-10V	3	
<b>10352</b>	STR8-60/DO/850-U-D	8'	6,000	46W	5000K	80+	120-277V	50,000	0-10V	3	

Continued on next page >>>



## STR: Linear Strip

Order Code	Item	Size	Lm	W	CCT	CRI	V	Life/Hrs L70	Dim	Photo #	DLC Premium
10353	STR8-85/D0/840-U-D	8'	8,500	65W	4000K	80+	120-277V	50,000	0-10V	3	
10354	STR8-85/D0/850-U-D	8'	8,500	65W	5000K	80+	120-277V	50,000	0-10V	3	
10355	STR8-117/D0/840-U-D	8'	11,700	90W	4000K	80+	120-277V	50,000	0-10V	3	
10356	STR8-117/D0/850-U-D	8'	11,700	90W	5000K	80+	120-277V	50,000	0-10V	3	

## STR: Accessories


Order Code	Item	Description
09823	STR-LCK	LED Strip, Linear Connection Kit
09788	STR-4-WG-W	Wire Guard, 4 ft. LED Strip, White
09849	FHSCP-UNV-5WL	5W Emergency Battery Backup
09851	FHSCP-UNV-7.8WL	7.8W Emergency Battery Backup

Order Code	Item	Description
10357	STR8-WG-W	Wire Guard 8' LED Strip White
09850	FHSCP-UNV-10.7WL	10.7W Emergency Battery Backup
09852	FHSCP-UNV-13.7WL	13.7W Emergency Battery Backup
09854	FHSCP-UNV-17WL	17W Emergency Battery Backup

## VTS: Vapor Tight Surface

Order Code	Item	Lm	W	CCT	CRI	V	Life/Hrs L70	MOL	Dim	Replaces Fluor.	Photo #	DLC Premium
09979	VTS-4-45/B0/850-DIM-U	4,400	40W	5000K	80+	120	50,000	50.24"	0-10V	(2) F32T8	4	✓
09714	VTS-4CS-40K-U	4,400	40W	4000K	80+	120-277	50,000	50.24"	0-10V	(2) F32T8	5	✓
09712	VTS-5CP-40K-U	5,200	40W	4000K	80+	120-277	50,000	50.24"	0-10V	(2) F32T8	5	✓✓
09977	VTS-4-52/D0/850-DIM-U	5,240	40W	5000K	80+	120	50,000	50.24"	0-10V	(2) F32T8	4	✓✓
09713	VTS-7CP-40K-U	6,760	52W	4000K	80+	120-277	50,000	50.24"	0-10V	(2) F54T5HO	5	✓✓
09978	VTS-4-68/D0/850-DIM-U	6,812	52W	5000K	80+	120	50,000	50.24"	0-10V	(2) F32T8	4	✓✓
09980	VTS-4-75/B5/850-DIM-U	7,150	65W	5000K	80+	120	50,000	50.24"	0-10V	(2) F32T8	4	✓
09715	VTS-7CS-40K-U	7,150	65W	4000K	80+	120-277	50,000	50.24"	0-10V	(2) F54T5HO	5	✓





## Troffer & Panel Fixtures

- Alternative LED solution to traditional fluorescent troffers
- Ultra-high-efficiency LEDs provide superior performance
- Choice of 3500K, 4000K, or 5000K
- Available in 2'x2' and 2'x4'
- Standard 0-10V dimming driver
- Universal input voltage (120-277V)
- 5 year system warranty

### VOL : Volumetric Troffer

Order Code	Item	Size	Lm	W	CCT	CRI	V	Life/Hrs L70	Dim	Replaces Fluor.	Photo #	DLC Premium
<b>09469</b>	VOL22-3C-35K-U	2'x2'	3,275	26W	3500K	80+	120	50,000	0-10V	3x 17WT8, 2U31T8	1	✓✓
<b>09491</b>	VOL22-3C-50K-U	2'x2'	3,275	26W	5000K	80+	120	50,000	0-10V	3x 17WT8, 2U31T8	1	✓✓
<b>09706</b>	VOL22-3CP-35K-U	2'x2'	3,224	26W	3500K	80+	120-277	50,000	0-10V	3x 17WT8, 2U31T8	1	✓✓
<b>09707</b>	VOL22-3CP-40K-U	2'x2'	3,250	26W	4000K	80+	120-277	50,000	0-10V	3x 17WT8, 2U31T8	1	✓✓
<b>09708</b>	VOL22-3CP-50K-U	2'x2'	3,276	26W	5000K	80+	120-277	50,000	0-10V	3x 17WT8, 2U31T8	1	✓✓
<b>09709</b>	VOL24-5CP-35K-U	2'x4'	5,796	46W	3500K	80+	120-277	50,000	0-10V	2x 32T8, 3x 32T8	2	✓✓
<b>09710</b>	VOL24-5CP-40K-U	2'x4'	5,796	46W	4000K	80+	120-277	50,000	0-10V	2x 32T8, 3x 32T8	2	✓✓
<b>09711</b>	VOL24-5CP-50K-U	2'x4'	5,796	46W	5000K	80+	120-277	50,000	0-10V	2x 32T8, 3x 32T8	2	✓✓

### VOL : Accessories

Order Code	Item	Description
<b>09849</b>	FHSCP-UNV-5WL	5W Emergency Battery Backup
<b>09851</b>	FHSCP-UNV-7.8WL	7.8W Emergency Battery Backup
<b>09850</b>	FHSCP-UNV-10.7WL	10.7W Emergency Battery Backup
<b>09852</b>	FHSCP-UNV-13.7WL	13.7W Emergency Battery Backup

Order Code	Item	Description
<b>09854</b>	FHSCP-UNV-17WL	17W Emergency Battery Backup
<b>09898</b>	VOL22-SMK-W	2x2 Surface Mount Kit, White
<b>09899</b>	VOL24-SMK-W	2x4 Surface Mount Kit, White



## SLM : Slim Panel

Order Code	Item	Size	Lm	W	CCT	CRI	V	Life/Hrs L70	Dim	Replaces Fluor.	Photo #	DLC/Premium
09760	SLM14-4CB-35K-U	1x4	3,750	30W	3500K	80+	100-277	50,000	0-10V	3x 17WT8, 2U31T8	3	✓✓
09761	SLM14-4CB-40K-U	1x4	3,750	30W	4000K	80+	100-277	50,000	0-10V	3x 17WT8, 2U31T8	3	✓✓
09762	SLM14-4CB-50K-U	1x4	3,750	30W	5000K	80+	100-277	50,000	0-10V	3x 17WT8, 2U31T8	3	✓✓
09485	SLM22-3C-35K-U	2x2	3,000	30W	3500K	80+	100-277	50,000	0-10V	3x 17WT8, 2U31T8	4	✓
09486	SLM22-3C-40K-U	2x2	3,000	30W	4000K	80+	100-277	50,000	0-10V	3x 17WT8, 2U31T8	4	✓
09487	SLM22-3C-50K-U	2x2	3,000	30W	5000K	80+	100-277	50,000	0-10V	3x 17WT8, 2U31T8	4	✓
10015	SLM22-3CB-35K-U	2x2	3,000	30W	3500K	80+	100-277	50,000	0-10V	3x 17WT8, 2U31T8	4	✓
10016	SLM22-3CB-40K-U	2x2	3,000	30W	4000K	80+	100-277	50,000	0-10V	3x 17WT8, 2U31T8	4	✓
10017	SLM22-3CB-50K-U	2x2	3,000	30W	5000K	80+	100-277	50,000	0-10V	3x 17WT8, 2U31T8	4	✓
10205	SLM22-40/AO/835-U-D	2x2	4,000	40W	3500K	80+	100-277V	50,000	0-10V	3x 17WT8, 2U31T8	4	✓
10209	SLM22-40/AO/840-H-D	2x2	4,000	40W	4000K	80+	120-347V	50,000	0-10V	3x 17WT8, 2U31T8	4	✓
10206	SLM22-40/AO/840-U-D	2x2	4,000	40W	4000K	80+	100-277V	50,000	0-10V	3x 17WT8, 2U31T8	4	✓
10210	SLM22-40/AO/850-H-D	2x2	4,000	40W	5000K	80+	120-347V	50,000	0-10V	3x 17WT8, 2U31T8	4	✓
10207	SLM22-40/AO/850-U-D	2x2	4,000	40W	5000K	80+	100-277V	50,000	0-10V	3x 17WT8, 2U31T8	4	✓
09763	SLM22-4CB-35K-U	2x2	3,750	30W	3500K	80+	100-277	50,000	0-10V	3x 17WT8, 2U31T8	4	✓✓
09764	SLM22-4CB-40K-U	2x2	3,750	30W	4000K	80+	100-277	50,000	0-10V	3x 17WT8, 2U31T8	4	✓✓
09765	SLM22-4CB-50K-U	2x2	3,750	30W	5000K	80+	100-277	50,000	0-10V	3x 17WT8, 2U31T8	4	✓✓
09754	SLM22-5CB-35K-U	2x2	5,000	40W	3500K	80+	100-277	50,000	0-10V	3x 17WT8, 2U31T8	4	✓✓
09755	SLM22-5CB-40K-U	2x2	5,000	40W	4000K	80+	100-277	50,000	0-10V	3x 17WT8, 2U31T8	4	✓✓
09756	SLM22-5CB-50K-U	2x2	5,000	40W	5000K	80+	100-277	50,000	0-10V	3x 17WT8, 2U31T8	4	✓✓
10211	SLM24-40/AO/835-U-D	2x4	4,000	40W	3500K	80+	100-277V	50,000	0-10V	2x 32T8, 3x 32T8	5	✓
10212	SLM24-40/AO/840-U-D	2x4	4,000	40W	4000K	80+	100-277V	50,000	0-10V	2x 32T8, 3x 32T8	5	✓
10213	SLM24-40/AO/850-U-D	2x4	4,000	40W	5000K	80+	100-277V	50,000	0-10V	2x 32T8, 3x 32T8	5	✓
10018	SLM24-4CB-35K-U	2x4	4,000	40W	3500K	80+	100-277	50,000	0-10V	2x 32T8, 3x 32T8	5	✓
10019	SLM24-4CB-40K-U	2x4	4,000	40W	4000K	80+	100-277	50,000	0-10V	2x 32T8, 3x 32T8	5	✓
10021	SLM24-4CB-50K-U	2x4	4,000	40W	5000K	80+	100-277	50,000	0-10V	2x 32T8, 3x 32T8	5	✓
10214	SLM24-50/AO/835-U-D	2x4	5,000	50W	3500K	80+	100-277V	50,000	0-10V	2x 32T8, 3x 32T8	5	✓
10218	SLM24-50/AO/840-H-D	2x4	5,000	50W	4000K	80+	120-347V	50,000	0-10V	2x 32T8, 3x 32T8	5	✓
10215	SLM24-50/AO/840-U-D	2x4	5,000	50W	4000K	80+	100-277V	50,000	0-10V	2x 32T8, 3x 32T8	5	✓
10219	SLM24-50/AO/850-H-D	2x4	5,000	50W	5000K	80+	120-347V	50,000	0-10V	2x 32T8, 3x 32T8	5	✓
10216	SLM24-50/AO/850-U-D	2x4	5,000	50W	5000K	80+	100-277V	50,000	0-10V	2x 32T8, 3x 32T8	5	✓
09488	SLM24-5C-35K-U	2x4	4,000	40W	3500K	80+	100-277	50,000	0-10V	2x 32T8, 3x 32T8	5	✓
09489	SLM24-5C-40K-U	2x4	4,000	40W	4000K	80+	100-277	50,000	0-10V	2x 32T8, 3x 32T8	5	✓
09490	SLM24-5C-50K-U	2x4	4,000	40W	5000K	80+	100-277	50,000	0-10V	2x 32T8, 3x 32T8	5	✓
09766	SLM24-5CB-35K-U	2x4	5,000	40W	3500K	80+	100-277	50,000	0-10V	2x 32T8, 3x 32T8	5	✓✓
09767	SLM24-5CB-40K-U	2x4	5,000	40W	4000K	80+	100-277	50,000	0-10V	2x 32T8, 3x 32T8	5	✓✓
09768	SLM24-5CB-50K-U	2x4	5,000	40W	5000K	80+	100-277	50,000	0-10V	2x 32T8, 3x 32T8	5	✓✓
09757	SLM24-6CB-35K-U	2x4	6,250	50W	3500K	80+	100-277	50,000	0-10V	2x 32T8, 3x 32T8	5	✓✓
09758	SLM24-6CB-40K-U	2x4	6,250	50W	4000K	80+	100-277	50,000	0-10V	2x 32T8, 3x 32T8	5	✓✓
09759	SLM24-6CB-50K-U	2x4	6,250	50W	5000K	80+	100-277	50,000	0-10V	2x 32T8, 3x 32T8	5	✓✓

## SLM : Accessories

Order Code	Item	Description	Order Code	Item	Description
10051	SLM14-CABLE-CB	SLM14 Cable for CB - 4 cables/set	10363	SLM22-SMK-A	SLM22 Surface Mounting Kit
10367	SLM14-RMK-A	SLM14 Recessed Mounting Kit	09693	SLM24-CABLE	SLM24 Cable Set, 6 cables/set
09905	SLM14-SM	SLM14 Surface Mount Kit White	10052	SLM24-CABLE-CB	SLM24 Cable for CB - 6 cables/set
10364	SLM14-SMK-A	SLM14 Surface Mounting Kit	10368	SLM24-RMK-A	SLM24 Recessed Mounting Kit
09692	SLM22-CABLE	SLM22 Cable Set, 4 cables/set	09695	SLM24-SM	SLM24 Surface Mount Kit White
10366	SLM22-RMK-A	SLM22 Recessed Mounting Kit	10365	SLM24-SMK-A	SLM24 Surface Mounting Kit
09694	SLM22-SM	SLM22 Surface Mount Kit White	10369	SLM-SCK-A	SLM22/14/24 Suspension Cable Kit





## Downlight Fixtures

- Ultra-efficient LED downlight kits designed for both retrofitting into existing downlights and new installation
- Integrated LEDs reduce energy consumption up to 80%
- Retrofit kits fit in many popular recessed downlight fixtures
- Lasts up to 30x longer than incandescent
- Choice of soft white, warm white and cool white CCT
- Instant-on, no warmup time
- 90 CRI versions available

### DKDS : Downlight Disk Surface Kit

Order Code	Item	Size	Lm	W	CCT	CRI	V	Life/Hrs L70	Replaces	Photo #	ES
09916	DKDS-4-12W/6.5/927-DIM-120	4'	650	12W	2700K	90+	120	50,000	75W BR	1	★
09917	DKDS-4-12W/6.5/930-DIM-120	4'	650	12W	3000K	90+	120	50,000	75W BR	1	★
10299	DKDS-4-12W/7.5/940-DIM-120	4'	750	12W	4000K	90+	120	50,000	75W BR	1	
10300	DKDS-4-12W/7.5/950-DIM-120	4'	750	12W	5000K	90+	120	50,000	75W BR	1	
09920	DKDS-6-15W/9.5/927-DIM-120	6'	950	15W	2700K	90+	120	50,000	90W BR	1	★
09921	DKDS-6-15W/9.5/930-DIM-120	6'	950	15W	3000K	90+	120	50,000	90W BR	1	★
10301	DKDS-6-15W/10.5/940-DIM-120	6'	1050	15W	4000K	90+	120	50,000	90W BR	1	
10302	DKDS-6-15W/10.5/950-DIM-120	6'	1050	15W	5000K	90+	120	50,000	90W BR	1	

### AK : Adjustable Neck Downlight

Order Code	Item	Size	Lm	W	CCT	CRI	V	Life/Hrs L70	Replaces	Photo #	ES
09524	AK4-8.5W827-DIM-G7 2PK	4"	500	9W	2700K	80+	120	25,000	50W BR	2	★
09525	AK6-12W827-DIM-G7 2PK	5/6"	800	12W	2700K	80+	120	25,000	65W BR	2	★



## CDR : Commercial Downlight Retrofit Kit

Order Code	Item	Size	Lm	W	CCT	CRI	V	Life/Hrs L70	Replaces	Photo #
10121	CDR-6-10/85/840-SSW-DIM-U	6"	1,000	12W	4000K	80+	100-277	50,000		3
10115	CDR-6-15/85/840-SSW-DIM-U	6"	1,500	18W	4000K	80+	100-277	50,000		3
10116	CDR-6-23/85/840-SSW-DIM-U	6"	2,400	27W	4000K	80+	100-277	50,000		3
10117	CDR-8-10/85/840-SSW-DIM-U	8"	1,000	12W	4000K	80+	100-277	50,000		3
10118	CDR-8-15/85/840-SSW-DIM-U	8"	1,500	18W	4000K	80+	100-277	50,000		3
10119	CDR-8-20/85/840-SSW-DIM-U	8"	2,000	24W	4000K	80+	100-277	50,000		3
10120	CDR-8-33/85/840-SSW-DIM-U	8"	3,500	40W	4000K	80+	100-277	50,000		3

## DSK : Slim Disk Downlight


Order Code	Item	Size	Lm	W	CCT	CRI	V	Life/Hrs L70	Replaces	Photo #	ES
09518	DSK-11W927-DIM-G7	5"	650	11W	2700K	90+	120	50,000	50W BR	4	★
09519	DSK-11W930-DIM-G7	5"	650	11W	3000K	90+	120	50,000	50W BR	4	★
09521	DSK-15W927-DIM-G7	7"	850	15W	2700K	90+	120	50,000	65W BR	4	★
09522	DSK-15W930-DIM-G7	7"	850	15W	3000K	90+	120	50,000	65W BR	4	★
09523	DSK-15W940-DIM-G7	7"	850	15W	4000K	90+	120	50,000	65W BR	4	★

## 4" Downlight Kit

Order Code	Item	Lm	W	CCT	CRI	V	Life/Hrs L70	Replaces	Photo #	ES
09677	LED-DK4-9W927-DIM-G7	600	9W	2700K	90+	120V	50,000	65W BR	5	★
09678	LED-DK4-9W930-DIM-G7	600	9W	3000K	90+	120V	50,000	65W BR	5	★
09679	LED-DK4-9W940-DIM-G7	600	9W	4000K	90+	120V	50,000	65W BR	5	★
09680	LED-DK4-9W950-DIM-G7	600	9W	5000K	90+	120V	50,000	65W BR	5	★
10315	DK4-10W/8/827-D-120-W/B	800	10W	2700K	80+	120V	50,000	65W BR	5	
10316	DK4-10W/8/830-D-120-W/B	800	10W	3000K	80+	120V	50,000	65W BR	5	
10317	DK4-10W/8/840-D-120-W/B	800	10W	4000K	80+	120V	50,000	65W BR	5	
10318	DK4-10W/8/850-D-120-W/B	800	10W	5000K	80+	120V	50,000	65W BR	5	
10337	DK4-13W/9/927-D-120-W/B	900	13W	2700K	90+	120V	50,000	65W BR	5	
10338	DK4-13W/9/930-D-120-W/B	900	13W	3000K	90+	120V	50,000	65W BR	5	
10339	DK4-13W/9/940-D-120-W/B	900	13W	4000K	90+	120V	50,000	65W BR	5	
10340	DK4-13W/9/950-D-120-W/B	900	13W	5000K	90+	120V	50,000	65W BR	5	
10319	DK4-13W/11/827-D-120-W/B	1,100	13W	2700K	80+	120V	50,000	65W BR	5	
10320	DK4-13W/11/830-D-120-W/B	1,100	13W	3000K	80+	120V	50,000	65W BR	5	
10321	DK4-13W/11/840-D-120-W/B	1,100	13W	4000K	80+	120V	50,000	65W BR	5	
10322	DK4-13W/11/850-D-120-W/B	1,100	13W	5000K	80+	120V	50,000	65W BR	5	

## 4" Rotatable Downlight


Order Code	Item	Lm	W	CCT	CRI	V	Life/Hrs L70	Replaces	Photo #	ES
09083	LED-DK4RT-11W830-DIM-G5	650	11W	3000K	80+	120	50,000	65W BR	6	★
09084	LED-DK4RT-11W840-DIM-G5	650	11W	4000K	80+	120	50,000	65W BR	6	★
09085	LED-DK6RT-11W830-DIM-G5	750	11W	3000K	80+	120	50,000	65W BR	6	★



## 6" Downlight Kit

Order Code	Item	Lm	W	CCT	CRI	V	Life/Hrs L70	Replaces	Photo #	ES
09681	LED-DK6-11W927-DIM-G7	700	11W	2700K	90+	120V	50,000	65W BR	7	★
09682	LED-DK6-11W930-DIM-G7	700	11W	3000K	90+	120V	50,000	65W BR	7	★
09683	LED-DK6-11W940-DIM-G7	700	11W	4000K	90+	120V	50,000	65W BR	7	★
09684	LED-DK6-11W950-DIM-G7	700	11W	5000K	90+	120V	50,000	65W BR	7	★
10341	DK6-12W/8/927-D-120-W/B	800	12W	2700K	90+	120V	50,000	65W BR	7	
10342	DK6-12W/8/930-D-120-W/B	800	12W	3000K	90+	120V	50,000	65W BR	7	
10343	DK6-12W/8/940-D-120-W/B	800	12W	4000K	90+	120V	50,000	65W BR	7	
10344	DK6-12W/8/950-D-120-W/B	800	12W	5000K	90+	120V	50,000	65W BR	7	
10323	DK6-12W/10/827-D-120-W/B	1,000	12W	2700K	80+	120V	50,000	65W BR	7	
10324	DK6-12W/10/830-D-120-W/B	1,000	12W	3000K	80+	120V	50,000	65W BR	7	
10325	DK6-12W/10/840-D-120-W/B	1,000	12W	4000K	80+	120V	50,000	65W BR	7	
10326	DK6-12W/10/850-D-120-W/B	1,000	12W	5000K	80+	120V	50,000	65W BR	7	
09685	LED-DK6-15W927-DIM-G7	1,100	15W	2700K	90+	120V	50,000	65W BR	7	★
09686	LED-DK6-15W930-DIM-G7	1,100	15W	3000K	90+	120V	50,000	65W BR	7	★
09687	LED-DK6-15W940-DIM-G7	1,100	15W	4000K	90+	120V	50,000	65W BR	7	★
09688	LED-DK6-15W950-DIM-G7	1,100	15W	5000K	90+	120V	50,000	65W BR	7	★
10327	DK6-15W/12.5/827-D-120-W/B	1,250	15W	2700K	80+	120V	50,000	65W BR	7	
10328	DK6-15W/12.5/830-D-120-W/B	1,250	15W	3000K	80+	120V	50,000	65W BR	7	
10331	DK6-15W/12.5/840-D-120-W/B	1,250	15W	4000K	80+	120V	50,000	65W BR	7	
10332	DK6-15W/12.5/850-D-120-W/B	1,250	15W	5000K	80+	120V	50,000	65W BR	7	
10345	DK6-18W/12.5/927-D-120-W/B	1,250	18W	2700K	90+	120V	50,000	100W BR	7	
10346	DK6-18W/12.5/930-D-120-W/B	1,250	18W	3000K	90+	120V	50,000	100W BR	7	
10347	DK6-18W/12.5/940-D-120-W/B	1,250	18W	4000K	90+	120V	50,000	100W BR	7	
10350	DK6-18W/12.5/950-D-120-W/B	1,250	18W	5000K	90+	120V	50,000	100W BR	7	
10333	DK6-18W/15/827-D-120-W/B	1,500	18W	2700K	80+	120V	50,000	100W BR	7	
10334	DK6-18W/15/830-D-120-W/B	1,500	18W	3000K	80+	120V	50,000	100W BR	7	
10335	DK6-18W/15/840-D-120-W/B	1,500	18W	4000K	80+	120V	50,000	100W BR	7	
10336	DK6-18W/15/850-D-120-W/B	1,500	18W	5000K	80+	120V	50,000	100W BR	7	





## Canopy Fixtures

- Cost-effective, solid-state solutions for canopy applications
- Replaces high-watt HID fixtures and/or fluorescent luminaires
- Available in round and square configurations
- 5 year limited warranty

### SCRG : Surface Canopy Round Garage

Order Code	Item	Lm	W	CCT	CRI	V	Life/Hrs L70	Replaces HID	Photo #	DLC
09959	SCRG-50/D0/840-DIM-U-S1B-W‡	5,200	40W	4000K	80+	100-277	50,000	250W	1	✓
09955	SCRG-50/D0/840-DIM-U-W	5,200	40W	4000K	80+	100-277	50,000	250W	1	✓
09960	SCRG-50/D0/850-DIM-U-S1B-W‡	5,200	40W	5000K	80+	100-277	50,000	250W	1	✓
09956	SCRG-50/D0/850-DIM-U-W	5,200	40W	5000K	80+	100-277	50,000	250W	1	✓
09961	SCRG-75/D0/840-DIM-U-S1B-W‡	8,100	60W	4000K	80+	100-277	50,000	400W	1	✓
09957	SCRG-75/D0/840-DIM-U-W	8,100	60W	4000K	80+	100-277	50,000	400W	1	✓
09962	SCRG-75/D0/850-DIM-U-S1B-W‡	8,100	60W	5000K	80+	100-277	50,000	400W	1	✓
09958	SCRG-75/D0/850-DIM-U-W	8,100	60W	5000K	80+	100-277	50,000	400W	1	✓

*‡Features integrated sensor*

### SCRG : Accessories

Order Code	Item	Description
10113	SEN-S1-RC2	Remote Control for S1B Sensors
09963	SCRG-3G-BRK	Quick Mount Bracket for 3G applications

Order Code	Item	Description
09908	SEN-S1A-KO	Sensor, OCC/PC/RC, IP65, 1/2" Knock Out Mount, Remote Controllable

### SCST : Slim Canopy

Order Code	Item	Lm	W	CCT	CRI	V	Life/Hrs L70	Replaces HID	Photo #	DLC
09952	SCST-140/B0/850-U-W	14,000	130W	5000K	70+	100-277	50,000	250-400W	2	✓
09953	SCST-140/B0/850-V-W	14,000	130W	5000K	70+	200-480	50,000	250-400W	2	✓
09954	SCST-160/B0/850-U-W	16,000	150W	5000K	70+	100-277	50,000	400-600W	2	✓





## Wallpack Fixtures

- Economical and energy-efficient solutions for general purpose wall mount lighting
- Durable, impact-resistant construction
- Easy to install
- 5 year system warranty

### DTD : Dusk to Dawn

Order Code	Item	Lm	W	CCT	CRI	V	Life/Hrs L70	Replaces HID	Photo #	DLC
<b>09579</b>	DTD-2C-50K-U	5,000	50W	5000K	80+	100-277	50,000	175-250W	1	✓
<b>09964</b>	DTD-95/CO/850-DIM-GY-U	9,500	120W	5000K	80+	100-277	50,000	400W	1	✓
<b>09965</b>	DTD-140/B5/850-DIM-GY-U	14,000	80W	5000K	80+	100-277	50,000	400W	1	✓


### WFA : Wallpack Flood ARCH

Order Code	Item	Lm	W	CCT	CRI	V	Life/Hrs L70	Replaces HID	Photo #	DLC
<b>08597</b>	WFAM-1C-U	1,600	22W	5000K	75	120-277	50,000	70-150W	2	✓
<b>08598</b>	WFAM-2C-U	3,100	40W	5000K	75	120-277	50,000	175-200W	2	
<b>08599</b>	WFAL-3C-U	7,100	90W	5000K	70	120-277	50,000	400W	3	

### WFA : Accessories

Order Code	Item	Description
<b>08706</b>	WFAL-SF	2- <sup>3</sup> / <sub>8</sub> " Slipfitter
<b>08707</b>	WFAL-UT	U-Bracket
<b>08704</b>	WFAM-KN	½" Knuckle

Order Code	Item	Description
<b>08703</b>	WFAM-SF	2- <sup>3</sup> / <sub>8</sub> " Slipfitter
<b>08705</b>	WFAM-UT	U-Bracket



### WMC : Wallpack Cube

Order Code	Item	Lm	W	CCT	CRI	V	Life/Hrs L70	Finish	Photo #	DLC
09810	WMC-2C-40K-U	1,900	20W	4000K	80+	120-277	50,000	Bronze	4	✓
09580	WMC-2C-50K-U	1,900	20W	5000K	80+	120-277	50,000	Bronze	4	✓
09811	WMC-3C-40K-U	2,850	30W	4000K	80+	120-277	50,000	Bronze	4	✓
09581	WMC-3C-50K-U	2,850	30W	5000K	80+	120-277	50,000	Bronze	4	✓

### WMG : Wallpack, Glass

Order Code	Item	Lm	W	CCT	CRI	V	Life/Hrs L70	Finish	Photo #	DLC
09802	WMG-1C-40K-U	3,200	30W	4000K	70+	100-277	50,000	Bronze	5	✓
09574	WMG-1C-50K-U	3,200	30W	5000K	70+	100-277	50,000	Bronze	5	✓
09807	WMG-2C-40K-V	4,600	40W	4000K	70+	347-480	50,000	Bronze	5	✓
09596	WMG-2C-50K-V	4,600	40W	5000K	70+	347-480	50,000	Bronze	5	✓
09803	WMG-2C-40K-U	5,800	50W	4000K	70+	100-277	50,000	Bronze	5	✓
09575	WMG-2C-50K-U	5,800	50W	5000K	70+	100-277	50,000	Bronze	5	✓
09804	WMG-3C-40K-U	7,000	60W	4000K	70+	100-277	50,000	Bronze	5	✓
09576	WMG-3C-50K-U	7,000	60W	5000K	70+	100-277	50,000	Bronze	5	✓
09805	WMG-4C-40K-U	9,800	80W	4000K	70+	100-277	50,000	Bronze	5	✓
09808	WMG-4C-40K-V	9,500	80W	4000K	70+	347-480	50,000	Bronze	5	✓
09577	WMG-4C-50K-U	9,800	80W	5000K	70+	100-277	50,000	Bronze	5	✓
09809	WMG-4C-50K-V	9,500	80W	5000K	70+	347-480	50,000	Bronze	5	✓
09806	WMG-5C-40K-U	13,000	120W	4000K	70+	100-277	50,000	Bronze	5	✓
09578	WMG-5C-50K-U	13,000	120W	5000K	70+	100-277	50,000	Bronze	5	✓

### WMG : Accessories

Order Code	Item	Description
08746	WP-347T	347V Step Down Transformer

### WPT : Wallpack, Trapezoid

Order Code	Item	Lm	W	CCT	CRI	V	Life/Hrs L70	Finish	Photo #	DLC
08595	WPT-1C-U	2,900	37W	5000K	70	120-277	50,000	Bronze	6	
09812	WPT1-55/840-BZ-U	5,500	50W	4000K	80+	120-277	50,000	Bronze	6	✓
09813	WPT1-55/850-BZ-U	5,500	50W	5000K	80+	120-277	50,000	Bronze	6	✓
09814	WPT1-88/840-BZ-U	8,800	80W	4000K	80+	120-277	50,000	Bronze	6	✓
09816	WPT1-88/840-BZ-V	8,800	80W	4000K	80+	347-480	50,000	Bronze	6	✓
09815	WPT1-88/850-BZ-U	8,800	80W	5000K	80+	120-277	50,000	Bronze	6	✓
09817	WPT1-88/850-BZ-V	8,800	80W	5000K	80+	347-480	50,000	Bronze	6	✓

### WPW : Wallpack Wedge

Order Code	Item	Lm	W	CCT	CRI	V	Life/Hrs L70	Finish	Photo #
08589	WPW-1C-120	800	11W	5000K	70	120	50,000	Bronze	7



## Occupancy Sensors

- Omni-directional quad-element sensors for energy-saving light control
- Available remote commissioning device
- Optional interchangeable lenses to adjust detection pattern; contact EiKO for more details
- 7 year limited warranty

### Occupancy Sensors

Order Code	Item	Description	Photo #
<b>09890</b>	SEN-3A-KO	PIR OCC/PC, On/Off, IP66, High Bay Lens, ½" Knock Out Mount	1
<b>10220</b>	SEN-3B-KO	PIR OCC/PC-DDC, IP66, High Bay Lens, ½" Knock Out Mount, 120-277V	1
<b>10221</b>	SEN-3C-KO	PIR OCC/PC-DDC, IP66, High Bay Lens, ½" Knock Out Mount, 347/480V	1
<b>09909</b>	SEN-S1-RC	Remote Control for S1A Sensors	2



# Miniature LED Replacement Lamps

- 30,000 hour rated life
- Low power consumption and high brightness
- Direct replacement for standard incandescent lamps
- Available in blister pack, two per card
- Energy efficient: costs less than other alternatives to operate over the life of the lamp
- Extreme long life: less frequent re-lamping reduces maintenance costs

## Miniature LED

Order Code	Item	V	Bulb	Base	Color	Replaces Incandescent	Photo #
02678	LED-120-MB-G	110-130VAC	T3-1/4	BA9s	Green	120MB, 120MB-6, 130MB, 8-3995, 949, 967	1
02679	LED-120-MB-R	110-130VAC	T3-1/4	BA9s	Red	120MB, 120MB-6, 130MB, 8-3995, 949, 967	1
02681	LED-120-MB-W	110-130VAC	T3-1/4	BA9s	White	120MB, 120MB-6, 130MB, 8-3995, 949, 967	1
02682	LED-120-MB-Y	110-130VAC	T3-1/4	BA9s	Yellow	120MB, 120MB-6, 130MB, 8-3995, 949, 967	1
02683	LED-120-PSB-G	110-130VAC	T2	TS5	Green	120PSB5, 120PSB-Neon	2
02684	LED-120-PSB-R	110-130VAC	T2	TS5	Red	120PSB5, 120PSB-Neon	2
02685	LED-120-PSB-W	110-130VAC	T2	TS5	White	120PSB5, 120PSB-Neon	2
02686	LED-120-PSB-Y	110-130VAC	T2	TS5	Yellow	120PSB5, 120PSB-Neon	2
05379	LED-12-DCBAY-W	12VAC/DC	S8	BAY15d	White	DC Index Bayonet Base 12V S8 Lamps	3
05385	LED-12-FESTOON-W	12VAC/DC	Festoon 10mm	SV8.5mm	White	10 x 44 Xenon Festoons	4
05394	LED-12-SCBAY-W	12VAC/DC	S8	BA15s	White	SC Bayonet Base 12V S8 Lamps	5
02687	LED-14-BA9S-G	14VAC/DC	T3-1/4	BA9s	Green	756, 1813, 1815, 1816, 1889, 1891, 1892, 1893	1
02688	LED-14-BA9S-R	14VAC/DC	T3-1/4	BA9s	Red	756, 1813, 1815, 1816, 1889, 1891, 1892, 1893	1
02689	LED-14-BA9S-W	14VAC/DC	T3-1/4	BA9s	White	756, 1813, 1815, 1816, 1889, 1891, 1892, 1893	1
02691	LED-14-T1.75 WEDGE-W	14VAC/DC	T1-3/4	W2.1x4.6d	White	18, 37, 70, 73, 74	6
00345	LED-194-W	14VAC/DC	T3-1/4	W2.1x9.5d	White	T3-1/4 Min Wedge Based Lamps 12/14V	7
02693	LED-24-BA9S-G	24-28VAC/DC	T3-1/4	BA9s	Green	24MB, 28MB, 313, 757, 1818, 1819, 1820, 1829, 1843, 1864, 1873	1
02694	LED-24-BA9S-R	24-28VAC/DC	T3-1/4	BA9s	Red	24MB, 28MB, 313, 757, 1818, 1819, 1820, 1829, 1843, 1864, 1873	1
02695	LED-24-BA9S-W	24-28VAC/DC	T3-1/4	BA9s	White	24MB, 28MB, 313, 757, 1818, 1819, 1820, 1843, 1829, 1864, 1873	1
02696	LED-24-BA9S-Y	24-28VAC/DC	T3-1/4	BA9s	Yellow	24MB, 28MB, 313, 757, 1818, 1819, 1820, 1843, 1829, 1864, 1873	1
05377	LED-24-FESTOON-W	24VDC	Festoon 10mm	SV8.5mm	White	10 x 44 Xenon Festoons	4
02698	LED-24-MF-W	24-28VAC/DC	T1-3/4	SX6s	White	327, 376, 385, 387, 7341	8
02702	LED-24-MG-W	24-28VAC/DC	T1-3/4	S5.7s	White	276, 334, 388	9
02704	LED-24-PSB-G	24-28VAC/DC	T2	TS5	Green	24PSB5, 28PSB5	2
02705	LED-24-PSB-R	24-28VAC/DC	T2	TS5	Red	24PSB5, 28PSB5	2
02706	LED-24-PSB-W	24-28VAC/DC	T2	TS5	White	24PSB5, 28PSB5	2
02707	LED-24-PSB-Y	24-28VAC/DC	T2	TS5	Yellow	24PSB5, 28PSB5	2
02709	LED-24-T1.75 WEDGE-R	24-28VAC/DC	T1-3/4	W2.1x4.6d	Red	17, 85	6
02711	LED-24-T1.75 WEDGE-W	24-28VAC/DC	T1-3/4	W2.1x4.6d	White	17, 85	6
02712	LED-24-T1.75 WEDGE-Y	24-28VAC/DC	T1-3/4	W2.1x4.6d	Yellow	17, 85	6
05742	LED-6-BA9S-W	6VAC/DC	T3-1/4	BA9s	White	6MB, 44, 47, 238, 755, 1810, 1847, 1866	1








## Guaranteed sale!

Move products out the door with EiKO's wire rack displays! Available in three recommended layouts and interchangeable header cards, you will have the option to pick and choose from our broad selection of replacement lamps and fixtures – all guaranteed to facilitate sales!

### LED Lamp and Fixture Merchandisers

Order Code	Item	Lamp Option	Fixture Option	Lamp & Fixture Option	Photo(s)
<b>09895</b>	LED9WA19/OMN/827-DIM-G8	2		2	 Lamp Option
<b>09896</b>	LED9WA19/OMN/830-DIM-G8	2		2	
<b>09752</b>	LED9WA19/OMN/840-DIM-G8	2		2	
<b>09886</b>	LED15WA19/OMN/827-DIM-G8	2			
<b>09944</b>	LED15WA19/OMN/830-DIM-G8	2			
<b>09945</b>	LED15WA19/OMN/840-DIM-G8	2			
<b>08936</b>	LED11WBR30/827K-DIM-G5	4		6	
<b>08937</b>	LED11WBR30/830K-DIM-G5	4		6	
<b>08938</b>	LED11WBR30/840K-DIM-G5	4		6	
<b>09514</b>	LED15WPAR38/FL/830-DIM-G7	4			
<b>09477</b>	LED12WPAR30S/FL/830-DIM-G7	4		2	 Fixture Option
<b>09156</b>	LED11WPAR30/FL/830K-DIM-G6	4			
<b>09185</b>	LED7WPAR20/FL/830K-DIM-G6	8			
<b>10229</b>	LED27WPT40KMED-G8	4		4	
<b>10250</b>	LED54WPT40KMOG-G8	4		4	
<b>10244</b>	LED45WPT40KMOG-G8	4			
<b>09878</b>	LED5WB11E26/FIL/827-DIM-G7	12			
<b>08732</b>	LED5WB11/E26/830-DIM-G5	12			
<b>08729</b>	LED5WB11/E12/827-DIM-G5	12			
<b>08730</b>	LED5WB11/E12/830-DIM-G5	12			
<b>09678</b>	LED-DK4-9W930-DIM-G7	8			 Lamp & Fixture Option
<b>09679</b>	LED-DK4-9W940-DIM-G7	8			
<b>09686</b>	LED-DK6-15W930-DIM-G7	8			
<b>09687</b>	LED-DK6-15W940-DIM-G7	8			
<b>09682</b>	LED-DK6-11W930-DIM-G7	12			
<b>09683</b>	LED-DK6-11W940-DIM-G7	12			
<b>09574</b>	WMG-1C-50K-U		6	4	
<b>09575</b>	WMG-2C-50K-U		6		
<b>09579</b>	DTD-2C-50K-U		6	4	
<b>09956</b>	SCRG-50/D0/850-DIM-U-W		4		
<b>09580</b>	WMC-2C-50K-U		2		
<b>09613</b>	FLJ-3C-30K-Y-U		4		

# EiKO USA: Terms, Conditions, & Shipping Procedures

**Effective:** January 15, 2018.

Supersedes all past terms and conditions of Price books and Sales Supplements.

**Prices:** As Shown and subject to change without notice.

**Distributor Status:** Distributors must purchase a minimum of \$3,500 annually in order to maintain distributor status.

**Small Order Charge:** Orders under \$250 will be assessed a \$15 small order charge (SOC).

**Payment Terms:** Net 30 days, from date of shipment as it appears on invoice. Postmark date on envelope will determine if payment has been made within terms. All orders received are subject to review and approval by our credit department. Orders received from customers with delinquent accounts may be subject to shipping delays, so please keep your account current.

**Freight:** NOTE: SoLux and EiKO products may be combined to meet prepaid freight requirements. EiKO Global, LLC will select the carrier of its choice.

1. All orders of \$1,000 or more will be shipped FREE FREIGHT F.O.B. destination via regular ground UPS, FedEx or USPS within the continental United States. Orders less than \$1,000 will be shipped F.O.B. origin.
2. UPS Second Day Air Blue – At the request of the distributor, orders will be billed at the UPS Second Day Air Rate.
3. UPS Next Day Air Red Label – At the request of the distributors, orders will be billed at the UPS Red Label Air rate.
4. Shipments made at the choice of the distributors, other than above, will be shipped F.O.B. shipping point.
5. Additional charges will apply for residential delivery.
6. Alaska, Hawaii and Puerto Rico – Orders of \$1,000 or more will be shipped free freight F.O.B. to a freight forwarder.
7. EiKO will no longer ship freight collect using the customer's account number.

We will cover the above items under normal Continental United States Policy. Therefore, you can achieve free freight to a border destination and then pick up the expense of forwarding the freight to your destination in Alaska, Hawaii or Puerto Rico. As an example, if you are a customer in Hawaii, you can have the goods for orders over \$1,000 shipped free freight to a freight forwarder. It would then be your responsibility to cover the freight to Hawaii.

## **Return Authorization:**

1. You must contact EiKO Global, LLC for authorization to return defective products and shipment errors.
2. Return authorization will not be issued unless the distributor provides a valid invoice number showing when goods were purchased. A copy of this invoice must be included with the return.
3. Goods must be less than one year old to be eligible for return.
4. Where the request for return is neither defective merchandise nor error made by EiKO Global, LLC, the following policy will apply: A restocking charge of 20% will be charged on all authorized and acceptable goods. If goods are not returned in resalable condition they will be returned to the sender at the expense of the sender and no credit will be issued.

NOTE: All returns must have a return number on the outside of the box or they will be refused.

**Shipment Discrepancies:** All shipment discrepancies, damage, etc, must be reported within 10 days of the shipment date shown on the invoice.

**General:** We reserve the right to, at any time and without notice, discontinue or substitute brands.

**Minimum Order Requirements for Linear Fluorescent Lamps:** In order to avoid breakage, the minimum order quantity for T8 & T12 linear fluorescent lamps four feet or longer is 360. The minimum order quantity for programmed start T5 linear fluorescent lamps is 100. Mixing SKUs to meet the minimum order is allowed. Orders under \$1,000 will be charged \$70 LTL freight.

**\*Important Note About Minimum Advertised Pricing (MAPP):** In order to avoid predatory pricing and to maintain the integrity of the products, SoLux products purchased through EiKO Global, LLC may not be advertised for sale (Internet, electronic, print media, mailings or otherwise) by you, a sub-distributor or any other agent, below the minimum advertised price established in the current Distributor Net Price Schedule. This minimum advertised price will be known as and referred to as the MAPP price. Failure to comply with MAPP pricing requirements will result in the loss of your access to SoLux products.

**EiKO Global, LLC:** 23220 W. 84th St, Shawnee, KS 66227 • Ph: 1.800.852.2217 • F: 1.913.441.6679 • email: eiko@eiko.com

eiko.com

# EiKO Canada: Terms, Conditions, & Shipping Procedures

**Effective:** May 1, 2018.

Supersedes all previously issued copies.

**Ordering:** All orders should be emailed to [orderdesk@eiko.com](mailto:orderdesk@eiko.com) or faxed to EiKO at 1-888-705-1335.

All orders received are subject to review and approval by our credit department.

**Distributor Status:** Distributors must purchase a minimum of \$2500.00 annually to maintain distributor status.

**Prices:** All prices are payable in Canadian funds. Prices are subject to change without notice and do not include applicable taxes. Any applicable taxes will be added to the invoice.

**Minimum Order:** \$75.00 minimum order requirement.

**Payment Terms:** Net 30 Days, from date of shipment as it appears on the invoice. Postmark date on envelope will determine if payment has been made within terms. All payments must be made in Canadian funds and mailed to below. EFT is available upon request.

EiKO Global, LLC (Canada)  
81 King Street  
Barrie, Ontario, L4N 6B5

**Freight Terms:** All pre-paid orders will be shipped F.O.B. destination via ground service and the carrier will be determined by EiKO. Orders that do not meet the pre-paid amount will be shipped at customer's expense. At the request and expense of customer, orders can be shipped via air service. At the request of customer, orders can be drop shipped and pre-paid amounts will apply to shipping destination.

F.O.B Destination, pre-paid as follows (before taxes):

British Columbia \$500.00	New Brunswick \$1,000.00
Alberta \$500.00	Nova Scotia \$1,000.00
Saskatchewan \$500.00	Prince Edward Island \$1,000.00
Manitoba \$750.00	Newfoundland and Labrador \$1,500.00
Ontario \$500.00	Yukon \$1,500.00
Montreal (Metropolitan Area) \$500.00	Northwest Territories \$1,500.00
All other points in Quebec \$750.00	Nunavut \$1,500.00

NOTE: - Pre-paid freight is \$1,000.00 in Alberta, British Columbia, Manitoba, Ontario, Quebec, and Saskatchewan when ordering product in length of 4 feet or longer.  
- Expedited ground freight is available upon request for Western Canada when shipping out of Ontario. Pre-paid freight is \$2000.00.

**Shipment Discrepancies/Damages:** EiKO will credit or replace product found to arrive in damaged or broken condition on all pre-paid freight orders. All shipment discrepancies, damage, etc., must be reported within 10 days of the shipment date shown on the invoice.

**Return Authorizations:** You must contact EiKO within 90 days of delivery for a Return Authorization number. An RA number will only be provided if the customer has a valid invoice showing when the goods were purchased from EiKO. Goods must be less than one year old to be eligible for return. All returns must be shipped pre-paid with a copy of the invoice and RA included. A restocking charge of 25% will be charged on all authorized and acceptable goods. An order of 2 times the return value will be accepted as an offset to the restocking charge. Goods returned not in original packaging and not in resalable condition will be returned to sender, at the expense of the sender, and no credit will be issued.

**General:** EiKO Canada Limited reserves the right to discontinue and substitute brands at any time without notice.

**EiKO Global Canada, LLC:** 81 King St, Barrie, ON L4N 6B5 • Ph: 1.705.721.5189 • F: 1.705.721.7855 • Email: [orderdesk@eiko.com](mailto:orderdesk@eiko.com)

[eiko.com](http://eiko.com)

# General Lighting Limited Warranty

EiKO brand lamps are warranted to be free of defective materials and workmanship for the period listed below. EiKO will replace or credit the distributor only for the cost of any lamp that fails under normal operating conditions and the use and operation conditions below due to defective materials or workmanship.

This warranty is limited to the replacement or credit of the lamp itself. This is buyer's exclusive remedy. Any other warranty, express or implied, including any warranty of merchantability or fitness for a particular purpose, is excluded and disclaimed. EiKO shall not be liable for any special, incidental or consequential damage including labor, loss of use, lost profits or injury to persons or property.

EiKO reserves the right to examine all lamps prior to the determination of warranty status. All lamps must be retained for warranty claims. The warranty period starts on the date of installation. If the date of installation is unknown or undetermined the warranty period will start at the wholesale purchase date.

Lamp Category	Warranty Period
LitespanLED® Line	60 months
Advantage™ Line	36 months
Metal Halide, High-Pressure Sodium, Mercury Vapor	15 months
Compact Fluorescent	12 months
Self Ballasted Compact Fluorescent	12 months
Linear Fluorescent (below 14 watt)	12 months
Linear Fluorescent (14 watt and above)	24 months
LCD	120 days

Credit is calculated as follows:

Credit (\$) = Invoiced Purchase Price (\$) x Unexpired Original Warranty Period (months)/Warranty Period

**Use and Operating Conditions:** Lamps must be used in UL approved fixtures with UL approved ballasts and installed according to local and national codes and standards. Use of occupancy sensors, dimmers or programmable systems with the lamp may void the warranty.

**HID Lamps:** Warranty is based on 5,000 hours per year maximum operation with a minimum of 8 hours operation per cycle. More frequent cycles will shorten lamp life and may not be covered under this warranty.

**Fluorescent Lamps:** Warranty is based on 4,000 hours per year maximum operation with a minimum of 3 hours operation per cycle. More frequent cycles will shorten lamp life and may not be covered under this warranty.

**Large Lamps:** Warranty is in effect for sales and installations on and after January 1, 2006.

**LED:** Warranty is in effect for sales and installations on and after July 1, 2010.

**LCD:** Warranty is in effect for sales and installations on and after July 1, 2009.

eiko.com

# EiKO LED Fixture Limited Warranty

EiKO branded LED Fixtures are warranted to be free of defective materials and workmanship for a period of not less than five years. EiKO LED Fixtures covered by this Limited Warranty shall be installed in accordance with the provided installation instructions as well as local and national codes and standards and utilized under normal operating conditions.

For any EiKO LED Fixture that fails to operate as indicated in the performance specifications defined in the documentation accompanying the EiKO LED Fixture or on published EiKO Specification sheets, and at EiKO's discretion, EiKO will replace, in part or whole, the EiKO LED Fixture or issue a credit to the distributor only for the cost of a Fixture due to defective materials or workmanship.

This warranty is limited to the replacement or credit of the fixture itself. This is buyer's exclusive remedy. Any other warranty, express or implied, including any warranty of merchantability or fitness for a particular purpose, is excluded and disclaimed. EiKO shall not be liable for any special, incidental or consequential damage including labor, loss of use, lost profits or injury to persons or property. Should EiKO provide replacement fixtures or components, EiKO reserves the right to utilize new, reconditioned, refurbished, repaired or remanufactured products or parts in the warranty replacement process. If EiKO chooses to replace the EiKO LED Fixture and is not able to do so because it has been discontinued or is not available, EiKO may replace the product with a comparable product. Furnishing of a replacement EiKO LED Fixture or a replacement part under the terms of this Limited Warranty shall not begin a new warranty period related to such replacement EiKO LED Fixture or part but rather shall be limited to the original warranty period associated with the warranted product.

EiKO reserves the right to examine all fixtures prior to the determination of warranty status. All fixtures must be retained for warranty claims until such time that EiKO determines the final disposition of the product. The warranty period starts on the date of installation. If the date of installation is unknown or undetermined the warranty period will start at the wholesale purchase date.

Credit is calculated as follows:  $\text{Credit (\$)} = \text{Invoiced Purchase Price (\$)} \times \frac{\text{Unexpired Original Warranty Period (months)}}{\text{Warranty Period}}$



watch > like > follow >



---

23220 W. 84<sup>th</sup> St, Shawnee, KS 66227 · (P) 1.800.852.2217 · (F) 1.800.492.8975  
Canada: 81 King St, Barrie, ON L4N 6B5 · (P) 1.888.410.8151 · (F) 1.888.705.1335